

UNIT	CONDENSER
MODEL #	eco-PMRC-682

**EVAPCO, INC.**




DWG. # CEWR122004-DRA-ST

REV -  
SERIAL #  
DATE: 2/20/2026

**NOTES:**


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C




FACE D

FACE B  
PLAN VIEW



FACE B



FACE A

SHIPPING  
WEIGHT

24540 lbs+ [11135] kg+

OPERATING  
WEIGHT

32130 lbs+ [14575] kg+

HEAVIEST SECTION  
WEIGHT

15590 lbs+ [7075] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG