

UNIT		CONDENSER		EVAPCO, INC. 	DWG. #	WB32M1808-DRC-ST	REV.	-
MODEL #	ATC-M494E	SCALE	NTS		SERIAL #		DATE	5/16/2026

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

1'-9 3/8" [543]

3'-9 1/4" * [1149]

2'-3/8" * [619]

7'-7" [2313]

12'-7 1/4" [3842]

2'-3" * [686]

(2) 4" [100] PE

REFRIG IN

(2) 4" [100] PE

REFRIG OUT

2" [50] MPT MAKE-UP

1'-11 1/8" [589]

3" [76]

5 1/4" [133]

4 1/4" [108]

5'-3 1/2" [1613]

7'-10" [2388]

2" [50] MPT DRAIN

3" [80] MPT OVERFLOW

6" [154] *

5'-1/4" [1529]

1'-3" [383]

FACE B

1'-7/8" [327]

1'-5" [432]

18'-0" [5486]

FACE A

SHIPPING WEIGHT	17080 lbs+ [7750] kg+	OPERATING WEIGHT	22610 lbs+ [10260] kg+	HEAVIEST SECTION WEIGHT	14350 lbs+ [6510] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	SLR
-----------------	-------------------------	------------------	--------------------------	-------------------------	-------------------------	--------------------------	---	-----------	-----