

UNIT COOLING TOWER		<div>EVAPCO, INC.</div> <div>evapco</div>	DWG. # T3040424-DRJ-ST	REV. -
MODEL # AT 14-2F4	SCALE NTS		SERIAL #	DATE 8/25/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

1'-3/4" [324]

2'-1/8" [613]

6'-5" [1956]

9'-6 1/2" [2908]

4" [100] MPT INLET

4" [100] MPT OUTLET

1" [25] MPT MAKE-UP

5 7/8" [149]

2" [50] MPT OVERFLOW

2" [50] MPT DRAIN

3'-1 1/2" [953]

1'-1" [330]

10 1/4" [260]

4 3/8" [111]

3" [76]

2'-1/4" [616]

5 1/8" [130]

4'-1/2" [1232]

1'-7 3/4" [502]

1'-1" [330]

FACE A

1'-1" [330]

4 1/2" [114]

6'-3" [1905]

3'-11 7/8" [1216]

SHIPPING WEIGHT 1130 lbs+ [515] kg+	OPERATING WEIGHT 1760 lbs+ [800] kg+	HEAVIEST SECTION WEIGHT 780 lbs+ [355] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: KWC
--	---	---	-------------------------------	------------------