

UNIT		COOLING TOWER		EVAPCO, INC. evapco	DWG. #	T36M1224-DRF-ST	REV.	-	
MODEL #	AT 220-2K12	SCALE	NTS		SERIAL #		DATE	11/22/2025	
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING. 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]					FACE C (2) ACCESS DOOR FACE D FACE A FACE B PLAN VIEW				
FACE B 20'-5/8" [6112] 1'-3 1/4" [387] 4'-10 7/8" [1495] 2'-1 1/4" [641] 9'-1" [2769] 7'-9 5/8" [2378] 9'-3/4" [2762] 9'-4 1/2" [2858] 9'-5 1/2" [2883] 9'-9 3/4" [2991] 5 1/8" [130] (2) 8" [200] BFW/GVD INLET (2) 8" [200] BFW/GVD OUTLET (2) 3" [80] MPT OVERFLOW (2) 2" [50] MPT MAKE-UP (2) 3" [80] MPT DRAIN					FACE A 11'-11 3/4" [3651] 1 3/8" [35] 6'-2 1/4" [1886] 8'-3" [2515] 14'-5 1/4" [4401] 7" [178] 2" [51] (M) (M)				
SHIPPING WEIGHT	13540 lbs+ [6145] kg+	OPERATING WEIGHT	23460 lbs+ [10645] kg+	HEAVIEST SECTION WEIGHT	4320 lbs+ [1960] kg+	NO. OF SHIPPING SECTIONS	4	DRAWN BY:	JLG