



| | | | | |
|------------------------------|--------------|--|---------------------------|-------------------|
| UNIT COOLING TOWER | | EVAPCO, INC.  | DWG. # T36M1848-DRF-ST | REV. - |
| MODEL # AT 220-4K18 | SCALE NTS | | SERIAL # | DATE 8/15/2025 |

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT
DRAWING
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE C


(2) ACCESS DOOR



FACE D




FACE A




FACE B

PLAN VIEW



FACE A



| | | | | | | | | | |
|-----------------|-----------------------|------------------|------------------------|-------------------------|----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 21980 lbs+ [9970] kg+ | OPERATING WEIGHT | 37180 lbs+ [16865] kg+ | HEAVIEST SECTION WEIGHT | 7080 lbs+ [3215] kg+ | NO. OF SHIPPING SECTIONS | 4 | DRAWN BY: | KDS |
|-----------------|-----------------------|------------------|------------------------|-------------------------|----------------------|--------------------------|---|-----------|-----|