

UNIT COOLING TOWER		EVAPCO, INC. evapco	DWG. # T3170948-DRG-ST	REV. -
MODEL # AT 217-4G9	SCALE NTS		SERIAL #	DATE 9/25/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT
DRAWING
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE C

(2) ACCESS DOOR

FACE B

PLAN VIEW

FACE D

FACE A

1'-9 3/8" [543]

(2) 8" [200] BFW/GVD INLET

1'-7/8" [327]

4'-2 3/4" [1289]

10'-3 1/2" [3137]

(2) 8" [200] BFW/GVD OUTLET

(2) 3" [80] MPT OVERFLOW

(2) 2" [50] MPT MAKE-UP

(2) 3" [80] MPT DRAIN

5 1/8" [130]

17'-4 1/8" [5286]

6'-8 1/4" [2038]

7'-8 1/2" [2350]

8'-1 1/4" [2445]

8'-1 1/4" [2470]

8'-5 1/2" [2578]

1'-11 1/8" [587]

1'-2 7/8" [378]

7 1/2" [190]

3 5/8" [92]

FACE B

2" [51]

9'-3 1/8" [2823]

14'-3 3/8" [4353]

5'-1/4" [1530]

1 3/8" [35]

8'-11 1/2" [2731]

FACE A

SHIPPING WEIGHT	9580 lbs+ [4350] kg+	OPERATING WEIGHT	15260 lbs+ [6925] kg+	HEAVIEST SECTION WEIGHT	3250 lbs+ [1475] kg+	NO. OF SHIPPING SECTIONS	4	DRAWN BY:	KDS
-----------------	----------------------	------------------	-----------------------	-------------------------	----------------------	--------------------------	---	-----------	-----