


UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3171208-DRD-ST	REV. -
MODEL # ATWB 17-4L12	SCALE NTS		SERIAL #	DATE 4/28/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE C





FACE D

FACE B

PLAN VIEW

FACE A





FACE B

SHIPPING WEIGHT

23480 lbs+ [10655] kg+

OPERATING WEIGHT

35480 lbs+ [16095] kg+

HEAVIEST SECTION WEIGHT

9940 lbs+ [4510] kg+

NO. OF SHIPPING SECTIONS

4

DRAWN BY:

SLR