

UNIT CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div>evapco</div>	DWG. # WB3242408-DRD-ST	REV. -
MODEL # ATWB 24-4L24	SCALE NTS		SERIAL #	DATE 9/13/2025

NOTES:  
1. (M)- FAN MOTOR LOCATION  
2. HEAVIEST SECTION IS UPPER SECTION  
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END  
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)  
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  
6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING  
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  
8. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

FACE A

2'-6 3/4" [ 781 ] \*

(8) 4" [100] BFW

FLUID IN

(8) 4" [100] BFW

FLUID OUT

2'-1 1/4" [ 643 ]

1'-5" [ 433 ]

3 5/8" [ 92 ]

(4) 3" [80] MPT OVERFLOW

(4) 2" [50] MPT MAKE-UP

(4) 3" [80] MPT DRAIN

5 1/8" [ 130 ]

24'-1 1/8" [ 7344 ]

5'-9 1/4" \* [ 1759 ]

3'-3/8" \* [ 924 ]

9'-1/8" [ 2748 ]

17'-2 3/8" [ 5242 ]

6" [ 154 ] \*

8'-2 1/4" [ 2494 ]

4'-8" [ 1422 ]

11'-4 3/4" [ 3473 ]

11'-5 3/4" [ 3499 ]

11'-10" [ 3607 ]

1'-3 1/4" [ 387 ]

(8) 1/2" [15] FPT VENT

1'-6 1/2" [ 470 ]

24'-2" [ 7366 ]

1'-6 1/2" [ 470 ]

SHIPPING WEIGHT	66940 lbs+ [30365] kg+	OPERATING WEIGHT	104720 lbs+ [47505] kg+	HEAVIEST SECTION WEIGHT	13940 lbs+ [6325] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SLR
-----------------	------------------------	------------------	-------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----