

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 		DWG. #	WB3244006-DRC-ST		REV.	-
MODEL #		ATWB 24-3M40		SCALE	NTS	SERIAL #			DATE	12/17/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)


5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE C




(4) ACCESS DOOR

FACE D

FACE B

PLAN VIEW

FACE A



FACE A

5'-9 1/4" [1759] *

3'-3/8" [924] *

7" [178]

8'-3 5/8" [2532]

16'-5 7/8" [5026]

6" [154] *

8'-2 1/4" [2494]

4'-8" [1422]

11'-4 3/4" [3473]

11'-5 3/4" [3499]

11'-10" [3607]

24'-1 1/8" [7344]

5 1/8" [130]

3 5/8" [92]

1'-5" [433]

2'-1 1/4" [643]

1'-10 1/4" [565] *

FLUID IN

FLUID OUT

FLUID IN

FLUID OUT

(8) 4" [100] BFW

(8) 4" [100] BFW

(8) 4" [100] BFW

(8) 4" [100] BFW

(4) 2" [50] MPT MAKE-UP

(4) 3" [80] MPT DRAIN

(4) 3" [80] MPT OVERFLOW

FACE B

SHIPPING WEIGHT

89740 lbs+ [40710] kg+

OPERATING WEIGHT

147800 lbs+ [67045] kg+

HEAVIEST SECTION WEIGHT

17900 lbs+ [8120] kg+

NO. OF SHIPPING SECTIONS

6

DRAWN BY:

SLR