

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. #	WB3241206-DRD-SF	REV.	-	
MODEL #		ATWB 24-3J12-Z			SCALE	NTS	SERIAL #		DATE

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE

ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE

FOR PRE-FABRICATION OF CONNECTING

PIPING

7. SERIES FLOW PIPING AND AUX. CROSSOVER

DRAIN BY OTHERS.

8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO

RECOMMENDED STEEL SUPPORT DRAWING.

9. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE C

(2) ACCESS DOOR