

UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. # WB3242410-DRD-SF		REV. -
MODEL # ATWB 24-5L24-Z	SCALE NTS		SERIAL #		DATE 3/12/2026
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS. 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [MM]					
FACE B PLAN VIEW			FACE C (4) ACCESS DOOR FACE D FACE A		
FACE B			FACE A		
SHIPPING WEIGHT 75660 lbs+ [34320] kg+			OPERATING WEIGHT 116680 lbs+ [52930] kg+		HEAVIEST SECTION WEIGHT 16120 lbs+ [7315] kg+
			NO. OF SHIPPING SECTIONS 6		DRAWN BY: JLG