


UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3243610-DRC-SF	REV. -
MODEL # ATWB 24-5036-Z	SCALE NTS		SERIAL #	DATE 11/8/2025

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [MM]

FACE B




FACE B

FACE A




FACE A

FACE C



FACE D



FACE B

PLAN VIEW

SHIPPING WEIGHT 109560 lbs+ [49700] kg+

OPERATING WEIGHT 171320 lbs+ [77710] kg+

HEAVIEST SECTION WEIGHT 23320 lbs+ [10580] kg+

NO. OF SHIPPING SECTIONS 6

DRAWN BY: JLG