INIT CLOSE	D CIRCUIT COOLER	EV	ADCO TI	NC eva	pco	DWG. #	WV030610-DRD-SF	REV.
10DEL # LRWB 3-	5G6-Z SCALE NTS	EV	APCO, II	VC.		SERIAL #		DATE 11/4/2025
GVD DENOTES GRO FLG DENOTES FLAN PE DENOTES PLAIN 3. +UNIT WEIGHT DON ACCESSORIES (SEE 4. 3/4" [19mm] DIA. MO RECOMMENDED ST	E PIPE THREAD ALE PIPE THREAD 'ELED FOR WELDING DOVED NGE I END		- 110253 , ,	•	FACE C			FACE D
	IMENSIONS DO NOT RICATION OF G. RESSURE 50 psi [344 kPa] MAX IG AND AUX. CROSSOVER					XXI 3"		
(2) 4" [100] BFW – FLUID IN	2':1	4'-10 1/2" [1487] 0 1/2" *		(2) 1/2" [15] FPT VENT SERIES FLOW F (BY OTHERS)	PIPING	_	4'-2" [1270]	-
(2) 4" [100] BFW FLUID OUT		7'- <u>-</u> [2 5 1/4" *		AUX. CROSSOVER (BY OTHERS) ACCESS DOOR	R DRAIN	AG	CCESS DOOR	5'-3 3/8" [1610]
2" [50] MPT OVERFLOW 2" [50] MPT DRAIN	3 7/8" [98] 3'-4 1/2" [1029] FACE B	3'-1/4" [919] 8 3/4" [222] - 2 5/8" - [67] - 6 5/8" [167]	1'-1 1/8"		5'-6" 1676] 10'-1 7/8 [3096	1" [25] MAKE-	MPT UP	1'-8 1/8" [511]
SHIPPING WEIGHT	3150 lbs+ [1430] kg+	OPERATING 46	690 lbs+ [2130] kg+	HEAVIEST SECTION WEIGHT	3150 lbs+ [1430] kg+	NO. OF S	HIPPING SECTIONS 1	DRAWN BY: