CLOSED CIRCUIT COOLER	EVAD	CO TNC EV	/apco	wg. # WV030610-DRD-SF	REV.
10DEL# LRWB 3-5H6-Z SCALE N	EVAP	CO, INC.	S	ERIAL #	DATE 11/4/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH [METRIC] 6. * - APPROXIMATE DIMENSIONS DO NOT	PLAN VIEW	1/2"	FACE C		FACE D
USE FOR PRE-FABRICATION OF CONNECTING PIPING. 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS			10'-1 7/8" [3096] <u>FACE A</u>		
11 1/4" * [286] * [1'-6"] [457] [286] * [286] * [29]	* 4'-10 1/2" [1487] -10 1/2" * [1487] 7'-10 3/4" [2407]	(BY OTHE	OVER DRAIN	ACCESS DOOR 1" [25] MPT MAKE-UP	5'-3 3/8" [1610]
SHIPPING 3200 lbs+ [1455] kg+	OPERATING 4740 lbs+ [2	[2155] kg+ HEAVIEST SECTION WEIGHT	3200 lbs+ [1455] kg+	NO. OF SHIPPING SECTIONS 1	DRAWN BY: