





UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WLE051808-DRD-SF	REV. -
MODEL # LSWE 5-4M18-Z	SCALE NTS		SERIAL #	DATE 12/13/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. HEAVIEST SECTION IS COIL SECTION 8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS				
 FACE B PLAN VIEW		 FACE C FACE A FACE D		
 FACE B		 FACE A		
SHIPPING WEIGHT	11410 lbs+ [5180] kg+	OPERATING WEIGHT	16890 lbs+ [7665] kg+	HEAVIEST SECTION WEIGHT
			7390 lbs+ [3355] kg+	NO. OF SHIPPING SECTIONS
			2	DRAWN BY: TLS