
DWG. # REV. UNIT **CLOSED CIRCUIT COOLER** WV050912-DRD-SF EVAPCO, INC. EVAPCO DATE<sub>11/26/2025</sub> MODEL # SERIAL # NTS eco-LRWB 5-6K9-Z NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD **FACE C** FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5'-5/8" [ 1540 ] 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO **FACE B FACE D** RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN **PLAN VIEW** 6. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING. 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS **FACE A** 1'-4 3/8" [ 416 ] (2) 4" [100] BFW 6'-3" [ 1905 ] (2) 1/2" [15] FPT VENT FLUID IN 5'-6" [ 1678 ] 3'-6" \* SERIES FLOW PIPING (2) 4" [100] BFW FLUID OUT (BY OTHERS) 8'-6 1/4" [ 2597 ] AUX. CROSSOVER DRAIN 6'-7 3/4" [ 2026 ] (BY OTHERS) 5 1/4" [ 133 ] **ACCESS** DOOR 3 1/4" TYP. →



HEAVIEST SECTION

WEIGHT

8800 lbs+ [3995] kg+

OPERATING

WEIGHT

12920 lbs+ [5865] kg+

8800 lbs+ [3995] kg+

**SHIPPING** 

WEIGHT

NO. OF SHIPPING SECTIONS

DRAWN BY: