

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. #	WB3041208-DRE-ST	REV.	-
MODEL #	eco-ATWB 4-4E12	SCALE	NTS		SERIAL #		DATE	12/16/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]								
FACE B PLAN VIEW					FACE C FACE D FACE A			
FACE B					FACE A			
SHIPPING WEIGHT					OPERATING WEIGHT		HEAVIEST SECTION WEIGHT	
6780 lbs+ [3080] kg+					9940 lbs+ [4510] kg+		5960 lbs+ [2705] kg+	
NO. OF SHIPPING SECTIONS					DRAWN BY:			
2					CAF			