


|                                      |              |                                                                                                        |                            |                   |
|--------------------------------------|--------------|--------------------------------------------------------------------------------------------------------|----------------------------|-------------------|
| UNIT<br><b>CLOSED CIRCUIT COOLER</b> |              | <b>EVAPCO, INC.</b>  | DWG. #<br>WB3091810-DRC-ST | REV.<br>-         |
| MODEL #<br>eco-ATWB 9-5J18           | SCALE<br>NTS |                                                                                                        | SERIAL #                   | DATE<br>3/25/2026 |


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]


  







|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 24810 lbs+ [11255] kg+ | OPERATING WEIGHT | 34660 lbs+ [15725] kg+ | HEAVIEST SECTION WEIGHT | 22020 lbs+ [9990] kg+ | NO. OF SHIPPING SECTIONS | 2 | DRAWN BY: | SLR |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|