

|                               |              |                                                                                                        |                            |                   |
|-------------------------------|--------------|--------------------------------------------------------------------------------------------------------|----------------------------|-------------------|
| UNIT<br>CLOSED CIRCUIT COOLER |              | <b>EVAPCO, INC.</b>  | DWG. #<br>WB3171212-DRD-ST | REV.<br>-         |
| MODEL #<br>eco-ATWB 17-6M12   | SCALE<br>NTS |                                                                                                        | SERIAL #                   | DATE<br>7/11/2026 |


  

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

**FACE C**




(2) ACCESS DOOR

**FACE B**

**PLAN VIEW**


**FACE D**

**FACE A**



(4) 1/2" [15] FPT VENT



1'-9 3/8" [543]

4'-3/4" [1238]

2'-2 3/8" [670]

8'-10" [2694]

13'-10 1/4" [4223]

3'-6" [1067]

4" 4" [100] BFW FLUID IN

4" 4" [100] BFW FLUID OUT

6" [154]

5'-1/4" [1529]

1'-11 1/8" [589]

3" [76]

(2) 2" [50] MPT MAKE-UP

(2) 2" [50] MPT DRAIN

(2) 3" [80] MPT OVERFLOW

8'-1/4" [2445]

8'-1 1/4" [2470]

8'-5 1/2" [2578]

5 1/8" [130]

17'-4 1/8" [5286]

2'-10 1/4" [870]

1'-3" [383]

**FACE B**

**FACE A**

1'-7/8" [327]

1'-3 5/8" [397]

11'-11 3/4" [3651]

|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 37520 lbs+ [17020] kg+ | OPERATING WEIGHT | 51760 lbs+ [23480] kg+ | HEAVIEST SECTION WEIGHT | 16890 lbs+ [7665] kg+ | NO. OF SHIPPING SECTIONS | 4 | DRAWN BY: | SLR |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|