

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. #		WB3242410-DRD-ST		REV.		-																																						
MODEL #		eco-ATWB 24-5L24			SCALE		NTS		SERIAL #		DATE		7/10/2026																																				
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]																																																	
FACE B PLAN VIEW					FACE C (4) ACCESS DOOR FACE D FACE A																																												
FACE B					FACE A																																												
SHIPPING WEIGHT					93420 lbs+ [42375] kg+					OPERATING WEIGHT					134400 lbs+ [60965] kg+					HEAVIEST SECTION WEIGHT					20560 lbs+ [9330] kg+					NO. OF SHIPPING SECTIONS					6					DRAWN BY:					SLR				