





UNIT		CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div></div>	DWG. #	WB3242812-DRC-ST		REV.	-			
MODEL #		eco-ATWB 24-6N28			SCALE	NTS		SERIAL #	DATE 9/12/2025			
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div> PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</div> <div>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>8. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> METRIC [mm]</div>												
<div>PLAN VIEW</div> <div></div>												
<div>FACE B</div> <div></div>					<div>FACE A</div> <div></div>							
SHIPPING WEIGHT	123640 lbs+ [56085] kg+		OPERATING WEIGHT	175460 lbs+ [79590] kg+		HEAVIEST SECTION WEIGHT	27800 lbs+ [12610] kg+		NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SLR