

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WB36M2408-DRC-ST		REV.	-
MODEL #		eco-ATWB 20-4I24			SCALE	NTS		SERIAL #	DATE 11/18/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE B

PLAN VIEW

FACE C

(4) ACCESS DOOR

FACE D

FACE A

7" [178]

4'-9" [1448] *

2'-6 3/8" * [772]

9'-1/8" [2748]

17'-2 3/8" [5242]

6" [154] *

8'-2 1/4" [2494]

3'-10" [1168]

9'-4 1/2" [2858]

9'-5 1/2" [2883]

9'-9 3/4" [2991]

5 1/8" [130]

20'-5/8" [6112]

2'-1 1/4" [643]

1'-5" [433]

3 5/8" [92]

2'-6 3/4" [781] *

8" 4" [100] BFW

FLUID IN

8" 4" [100] BFW

FLUID OUT

(4) 2" [50] MPT MAKE-UP

(4) 3" [80] MPT DRAIN

(4) 3" [80] MPT OVERFLOW

FACE B

1'-3 1/4" [387]

(8) 1/2" [15] FPT VENT

1'-5" [432]

24'-2" [7366]

1'-5" [432]

FACE A

SHIPPING WEIGHT	69380 lbs+ [31475] kg+	OPERATING WEIGHT	102000 lbs+ [46270] kg+	HEAVIEST SECTION WEIGHT	14640 lbs+ [6645] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SLR
-----------------	------------------------	------------------	-------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----