

|                               |              |                                                                                                        |                            |                   |
|-------------------------------|--------------|--------------------------------------------------------------------------------------------------------|----------------------------|-------------------|
| UNIT<br>CLOSED CIRCUIT COOLER |              | <b>EVAPCO, INC.</b>  | DWG. #<br>WB36M2408-DRC-ST | REV.<br>-         |
| MODEL #<br>eco-ATWB 20-4M24   | SCALE<br>NTS |                                                                                                        | SERIAL #                   | DATE<br>6/20/2025 |


  

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

**PLAN VIEW**






**FACE B**



**FACE A**

|                                           |                                             |                                                  |                               |                  |
|-------------------------------------------|---------------------------------------------|--------------------------------------------------|-------------------------------|------------------|
| SHIPPING WEIGHT<br>70460 lbs+ [31965] kg+ | OPERATING WEIGHT<br>103080 lbs+ [46760] kg+ | HEAVIEST SECTION WEIGHT<br>14910 lbs+ [6765] kg+ | NO. OF SHIPPING SECTIONS<br>6 | DRAWN BY:<br>SLR |
|-------------------------------------------|---------------------------------------------|--------------------------------------------------|-------------------------------|------------------|