

UNIT		CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #	WB3091808-DRC-SF	REV.	-	
MODEL #		eco-ATWB 9-4H18-Z			SCALE	NTS		SERIAL #	DATE
<div>NOTES:</div> <div>1. (M) - FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div> PE DENOTES PLAIN END</div> <div>4. + UNIT WEIGHT DOES NOT INCLUDE</div> <div> ACCESSORIES (SEE SEPARATE DRAWINGS</div> <div> FOR ACCESSORIES)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. * - APPROXIMATE DIMENSIONS DO NOT USE</div> <div> FOR PRE-FABRICATION OF CONNECTING</div> <div> PIPING</div> <div>7. SERIES FLOW PIPING AND AUX. CROSSOVER</div> <div> DRAIN BY OTHERS</div> <div>8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO</div> <div> RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>9. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> METRIC [mm]</div>									
<div>FACE B</div> <div>PLAN VIEW</div>					<div>FACE C</div> <div>ACCESS DOOR</div> <div>ACCESS DOOR</div> <div>FACE D</div> <div>FACE A</div>				
<div>FACE B</div>					<div>FACE A</div>				
<div>SHIPPING WEIGHT</div> <div>21300 lbs+ [9665] kg+</div>					<div>OPERATING WEIGHT</div> <div>30310 lbs+ [13750] kg+</div>				
<div>HEAVIEST SECTION WEIGHT</div> <div>18510 lbs+ [8400] kg+</div>					<div>NO. OF SHIPPING SECTIONS</div> <div>2</div>				
<div>DRAWN BY:</div> <div>JLG</div>									