





UNIT		CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div></div>	DWG. #		WB3242406-DRD-SF		REV.		-								
MODEL #		eco-ATWB 24-3M24-Z			SCALE		NTS		SERIAL #		DATE		9/16/2025						
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div> PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE</div> <div> ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE</div> <div> FOR PRE-FABRICATION OF CONNECTING</div> <div> PIPING</div> <div>7. SERIES FLOW PIPING AND AUX. CROSSOVER</div> <div> DRAIN BY OTHERS.</div> <div>8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO</div> <div> RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>9. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> METRIC [MM]</div>																			
<div>FACE B</div> <div>PLAN VIEW</div>					<div>FACE C</div> <div>(4) ACCESS DOOR</div> <div></div> <div>FACE D</div>														
<div>FACE B</div> <div></div> <div>FACE A</div>					<div>FACE A</div> <div></div> <div>FACE A</div>														
SHIPPING WEIGHT		68700 lbs+ [31165] kg+		OPERATING WEIGHT		103200 lbs+ [46815] kg+		HEAVIEST SECTION WEIGHT		14380 lbs+ [6525] kg+		NO. OF SHIPPING SECTIONS		6		DRAWN BY:		JLG	