



UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB36M2412-DRC-SF	REV. -
MODEL # eco-ATWB 20-6I24-Z	SCALE NTS		SERIAL #	DATE 9/17/2025

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE C




(4) ACCESS DOOR

FACE B

FACE D

PLAN VIEW

FACE A



1'-3 1/4" [387]

(16) 1/2" [15] FPT VENT


SERIES FLOW PIPING (SEE NOTE 7)

AUX. CROSSOVER DRAIN (SEE NOTE 7)

24'-2" [7366]

1'-5" [432]

1'-5" [432]



(16) 4" [100] BFW FLUID IN

3'-11 3/4" [1213]

2'-1 1/4" [643]

1'-5" [433]

3 5/8" [92]

(4) 3" [80] MPT OVERFLOW

(4) 2" [50] MPT MAKE-UP

(4) 3" [80] MPT DRAIN

5 1/8" [130]

20'-5/8" [6112]

4'-9" [1448]

2'-6 3/8" [772]

10'-5 1/8" [3180]

18'-7 3/8" [5674]

6" [154]

8'-2 1/4" [2494]

9'-4 1/2" [2858]

9'-5 1/2" [2883]

9'-9 3/4" [2991]

3'-10" [1168]

SHIPPING WEIGHT	89780 lbs+ [40725] kg+	OPERATING WEIGHT	127680 lbs+ [57915] kg+	HEAVIEST SECTION WEIGHT	19740 lbs+ [8955] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SLR
-----------------	------------------------	------------------	-------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----