

UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco	DWG. # CW4C070912-DRA-SF		REV. -										
MODEL # eco-ATWB 7-6J9-Z		SCALE NTS			SERIAL #		DATE 8/27/2025										
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS. 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]					FACE B PLAN VIEW FACE C (M) ACCESS DOOR FACE D FACE A												
1'-9 3/8" [543] 3'-6 1/4" * [1073] 1'-10 7/8" * [581] 2'-11 3/8" [899] 13'-2 5/8" [4029] 5'-11 3/8" [1813] 4'-3 7/8" [1318] 1'-3" [381] 7'-4" [2235] 5'-3 5/8" [1616] 1'-11 1/8" [587] 2" [50] MPT MAKE-UP 2" [50] MPT DRAIN 3" [76] 5 1/4" [132] 4 1/4" [107] 3" [80] MPT OVERFLOW 3'-6" * [1067] (2) 4" [100] BFW FLUID IN (2) 4" [100] BFW FLUID OUT 5 1/4" * [133] (M)					1'-2" [356] (2) 1/2" [15] FPT VENT SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7) 1'-3 3/4" [400] 8'-11 1/2" [2731] FACE A												
SHIPPING WEIGHT		13340 lbs+ [6055] kg+		OPERATING WEIGHT		16960 lbs+ [7695] kg+		HEAVIEST SECTION WEIGHT		11750 lbs+ [5330] kg+		NO. OF SHIPPING SECTIONS		2		DRAWN BY: TAM	