

EVAPCO, INC.





| | | | | | | |
|---------------|-------------|--------|------------------|------|----------|----------|
| UNIT | MODEL # | SCALE | DWG. # | REV. | DATE | SERIAL # |
| COOLING TOWER | LSTE-10224U | N.T.S. | TLETM2436-DRA-ST | - | 9/5/2025 | |


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS LOWER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED FOR VICTAULIC
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN
[METRIC] [mm]

**FACE 1
PLAN VIEW**



FACE 1



| | | | | | | | |
|-----------------|-----------------------|------------------|------------------------|-------------------------|----------------------|--------------------------|---|
| SHIPPING WEIGHT | 16060 lbs+ [7285] kg+ | OPERATING WEIGHT | 28240 lbs+ [12809] kg+ | HEAVIEST SECTION WEIGHT | 9580 lbs+ [4345] kg+ | NO. OF SHIPPING SECTIONS | 3 |
|-----------------|-----------------------|------------------|------------------------|-------------------------|----------------------|--------------------------|---|