UNIT CONDENSER		T	EVADCO TNIC EVEDCO DWG. # WB3123612-DRC-ST	REV.
MODEL #	eco-ATC-1416A	SCALE NTS	EVAPCO, INC. EVAPCO WB3123612-DRC-ST	DATE 7/8/2025
2. HEAV 3. MPT I FPT I BFW GVD FLG I PE DI 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APF FOR I PIPIN 7. 3/4" [RECC	FAN MOTOR LOCATION //IEST SECTION IS UPPER SEI DENOTES MALE PIPE THREA DENOTES FEMALE PIPE THRI DENOTES BEVELED FOR WE DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END T WEIGHT DOES NOT INCLUE ESSORIES (SEE ACCESSORY E-UP WATER PRESSURE II MIN [137 kPa], 50 psi MAX [34 PROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONN	DE DRAWINGS) 44 kPa] NOT USE ECTING S. REFER TO DRAWING.	FACE B PLAN VIEW FACE A FACE A FACE A	FACE D
	3'-11 3/4" * [1213] (4) 4" [100] PE 2) 2" [50] MPT — MAKE-UP	REFRIG OUT O (154)	10'-5 1/8" [3180] 17'-7 3/8" [5369] * 7'-2 1/4" [2189]	

1'-11 1/8" <u>-</u> [587]

11'-10" [3607]

FACE B

36'-2 1/2" ₋ [11036]

FACE A