



UNIT		CONDENSER		EVAPCO, INC. 	DWG. #	EG091412-DRC-ST	REV.	-
MODEL #		eco-ATC-504A			SCALE	NTS	SERIAL #	DATE 6/23/2026
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]								
FACE B PLAN VIEW					FACE C ACCESS DOOR FACE D FACE A			
								
FACE B					FACE A			
SHIPPING WEIGHT	21440 lbs+ [9730] kg+		OPERATING WEIGHT	26580 lbs+ [12060] kg+		HEAVIEST SECTION WEIGHT	19360 lbs+ [8785] kg+	
						NO. OF SHIPPING SECTIONS	2	
						DRAWN BY: JLG		