

**CONFIDENTIAL**


This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

|          |                                 |              |                     |        |                |
|----------|---------------------------------|--------------|---------------------|--------|----------------|
| CUSTOMER | MODEL # U-SSTME1-14104H0150H1JA | SCALE N.T.S. | DWG. # USSTM1-SE-24 | REV. 0 | DATE 7/18/2026 |
|----------|---------------------------------|--------------|---------------------|--------|----------------|



NEMA 4X  
JUNCTION BOX

84 3/8  
6 \* 42 36 3/8




2" MPT  
DRAIN

5 3/4 42 38 5/8

**NOTES:**

- 1) \* = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.



AIR  
FLOW

45 3/8  
3/4 \* 41 3/8 3/4  
4 7/8  
58 1/2 65 1/2  
1 1/4 55 1 1/4  
57 1/2

|         |      |                                     |                                      |
|---------|------|-------------------------------------|--------------------------------------|
| PROJECT | ROOM | SHIPPING WEIGHT 1000 lbs+ [455] kg+ | OPERATING WEIGHT 1170 lbs+ [535] kg+ |
|---------|------|-------------------------------------|--------------------------------------|