


**CONFIDENTIAL**


This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

|          |                        |        |              |      |           |
|----------|------------------------|--------|--------------|------|-----------|
| CUSTOMER | MODEL #                | SCALE  | DWG. #       | REV. | DATE      |
|          | U-SSTME1-1443H0075F1JA | N.T.S. | USSTM1-SE-24 | 0    | 11/6/2025 |



NEMA 4X  
JUNCTION BOX

84 3/8  
6 \* 42 36 3/8




2" MPT  
DRAIN

5 3/4 42 38 5/8

**NOTES:**

- 1) \* = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.



45 3/8  
3/4 \* 41 3/8 3/4  
4 7/8  
58 1/2 65 1/2  
1 1/4 55 1 1/4  
57 1/2

|         |      |                    |                    |
|---------|------|--------------------|--------------------|
| PROJECT | ROOM | SHIPPING WEIGHT    | OPERATING WEIGHT   |
|         |      | 660 lbs+ [300] kg+ | 720 lbs+ [330] kg+ |