UNIT CONDENSER		EVAPCO, INC. Evapeo		vap co	OWG. # CEWR122408-DRA-ST	REV	-
MODEL# eco-PMRC-1000 SCALE N	rs	EVAPCO, I	IVC.	S	ERIAL#	DATE:	11/26/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.		FACE E PLAN VIE	- - 17188888		CE A		FACE D
3'-0 7/8" * 5'-8 ! [937]	(2) 3"[80] MPT OVERFLOW	2'-6 3/4" [781] * 5'-9 5/8" [' 14'-4" [4369] 9'-11" [3023] * 8'-6 3/8" [2	2600]		7/8"		—1'-6" [457]
SHIPPING WEIGHT 42500 lbs+ [19280] kg+	OPERATING	52350 lbs+ [23750] kg+	HEAVIEST SECTION	15900 lbs+ [7215] kg+		DRAWN BY:	JLG
WEIGHT 42300 IDST [19200] NGT	WEIGHT	OZOOU IDST [ZO10U] NYT	WEIGHT	10000 100+ [1210] Kg+	J		010