

UNIT	CONDENSER
MODEL #	eco-PMRC-1000

**EVAPCO, INC.**




DWG. # CEWR122408-DRA-ST

REV -  
SERIAL #  
DATE: 2/19/2026

**NOTES:**


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BEW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

**FACE C**




**FACE D**

**FACE B**  
**PLAN VIEW**



**FACE B**



**FACE A**

SHIPPING  
WEIGHT

42500 lbs+ [19280] kg+

OPERATING  
WEIGHT

52350 lbs+ [23750] kg+

HEAVIEST SECTION  
WEIGHT

15900 lbs+ [7215] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: JLG