

UNIT	CONDENSER
MODEL #	eco-PMRC-889

EVAPCO, INC.



DWG. # CEWR122006-DRA-ST

REV -


SERIAL #

DATE: 2/19/2026

NOTES:

1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.


FACE C




FACE D

FACE B

PLAN VIEW



FACE B



FACE A

SHIPPING
WEIGHT

30420 lbs+ [13800] kg+

OPERATING
WEIGHT

38170 lbs+ [17315] kg+

HEAVIEST SECTION
WEIGHT

21090 lbs+ [9570] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG