

Evapco EAW Line Thermal Performance in USGPM - Water as Process Fluid

Range °F	10	10	15	15	9	10	10	15	15	9	First	First	Second	Second	Second	Third	Third	Third	
Approach °F	5	10	10	12	18	5	10	10	12	18	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow	
Dry Bulb Temperature °F	77	77	77	77	77	95	95	95	95	95	GPM	PSI	Flow Inlet	GPM	PSI	Flow Inlet	GPM	PSI	
EAW-DD1504XL017G7-525AXSP08	372.6	585.6	447.5	503.3	980.7	373.3	583.4	446.1	501.4	972.3	654	14.2	4"	523	9.4	4"	784	19.9	4"
EAW-DD1504XL017G7-625AXSP12	427.2	651.2	503.4	562.5	-	425.9	646.6	500.5	559.2	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD1504XL017G7-632AXSP12	400.2	615.1	473.3	529.6	-	398.5	610.6	470.6	526.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD1508XL017G7-525AXSP04	742.5	1167.6	890.5	1001.7	1956	744.1	1161.6	889.2	999.7	1939.2	1319	16	4"	1055	10.5	4"	1582	18.2	6"
EAW-DD1508XL017G7-625AXSP06	849.4	1295.6	1001	1118.7	-	848	1286.3	996.8	1112.1	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD1508XL017G7-632AXSP06	795.3	1223.1	940.7	1054.2	-	793.1	1214.2	936.8	1048	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD1512XL017G7-525AXSP04	1158.9	1789	1374.2	1541.7	-	1156.4	1776.5	1366.9	1533.1	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD1512XL017G7-625AXSP04	1268.3	1935.5	1494.9	1670.9	-	1264.6	1921.8	1486.5	1661.2	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD1512XL017G7-632AXSP04	1185.1	1824	1404.3	1571.6	-	1182.1	1813.5	1396.4	1562.4	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3351XL030M3-525AXSP12	326.8	500.7	385.6	431.7	-	325.4	496.3	383.4	428.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030M3-625AXSP12	360.6	545.7	423.3	472.1	-	359.3	540.9	420.7	468.5	880	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M3-632AXSP12	339.2	517.5	399.9	447.1	850.6	337.4	513.4	397.3	443.5	841.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M4-525AXSP12	326.8	500.7	385.6	431.7	-	325.4	496.3	383.4	428.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030M4-625AXSP12	360.6	545.7	423.3	472.1	-	359.3	540.9	420.7	468.5	880	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M4-632AXSP12	339.2	517.5	399.9	447.1	850.6	337.4	513.4	397.3	443.5	841.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M5-525AXSP12	326.8	500.7	385.6	431.7	-	325.4	496.3	383.4	428.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030M5-625AXSP12	360.6	545.7	423.3	472.1	-	359.3	540.9	420.7	468.5	880	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M5-632AXSP12	339.2	517.5	399.9	447.1	850.6	337.4	513.4	397.3	443.5	841.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M9-525AXSP12	326.8	500.7	385.6	431.7	-	325.4	496.3	383.4	428.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030M9-625AXSP12	360.6	545.7	423.3	472.1	-	359.3	540.9	420.7	468.5	880	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030M9-632AXSP12	339.2	517.5	399.9	447.1	850.6	337.4	513.4	397.3	443.5	841.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N3-525AXSP12	315.5	482.6	372.1	416.4	-	313.8	478.6	369.7	412.9	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030N3-625AXSP12	348.4	526.6	408.8	455.8	857.3	346.6	521.3	405.8	451.8	846.7	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N3-632AXSP12	326.9	498.8	385.8	431.2	819.2	325.4	494.5	383.1	427.4	809.8	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N4-525AXSP12	315.5	482.6	372.1	416.4	-	313.8	478.6	369.7	412.9	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030N4-625AXSP12	348.4	526.6	408.8	455.8	857.3	346.6	521.3	405.8	451.8	846.7	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N4-632AXSP12	326.9	498.8	385.8	431.2	819.2	325.4	494.5	383.1	427.4	809.8	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N5-525AXSP12	315.5	482.6	372.1	416.4	-	313.8	478.6	369.7	412.9	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030N5-625AXSP12	348.4	526.6	408.8	455.8	857.3	346.6	521.3	405.8	451.8	846.7	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N5-632AXSP12	326.9	498.8	385.8	431.2	819.2	325.4	494.5	383.1	427.4	809.8	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N9-525AXSP12	315.5	482.6	372.1	416.4	-	313.8	478.6	369.7	412.9	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030N9-625AXSP12	348.4	526.6	408.8	455.8	857.3	346.6	521.3	405.8	451.8	846.7	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030N9-632AXSP12	326.9	498.8	385.8	431.2	819.2	325.4	494.5	383.1	427.4	809.8	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030Q3-525AXSP12	315.5	482.6	372.1	416.4	-	313.8	478.6	369.7	412.9	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030Q3-625AXSP12	348.4	526.6	408.8	455.8	857.3	346.6	521.3	405.8	451.8	846.7	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030Q3-632AXSP12	326.9	498.8	385.8	431.2	819.2	325.4	494.5	383.1	427.4	809.8	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030T3-525AXSP12	326.8	500.7	385.6	431.7	-	325.4	496.3	383.4	428.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030T3-625AXSP12	360.6	545.7	423.3	472.1	-	359.3	540.9	420.7	468.5	880	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030T3-632AXSP12	339.2	517.5	399.9	447.1	850.6	337.4	513.4	397.3	443.5	841.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X3-525AXSP12	317.9	487.2	375.6	420.3	-	316.5	483	373.5	417.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030X3-525AXSP16	320.9	487.9	377.3	421.6	-	319	483.7	374.6	418.5	-	316	26.7	4"	252	17.7	4"	379	37.5	4"
EAW-DD3351XL030X3-625AXSP12	350.4	529.8	411.2	458.6	862.5	348.6	525.1	408.1	455.1	852.9	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X3-625AXSP16	355.8	533.7	415.7	462.2	-	353.4	528.3	412	458.6	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL030X3-632AXSP12	329.8	503.5	389.4	434.6	827	328.2	499	386.4	431.9	817.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X3-632AXSP16	334.8	507.6	393.4	438.9	-	332.6	503	390.4	434.9	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL030X4-525AXSP12	317.9	487.2	375.6	420.3	-	316.5	483	373.5	417.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030X4-625AXSP12	350.4	529.8	411.2	458.6	862.5	348.6	525.1	408.1	455.1	852.9	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X4-632AXSP12	329.8	503.5	389.4	434.6	827	328.2	499	386.4	431.9	817.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X5-525AXSP12	317.9	487.2	375.6	420.3	-	316.5	483	373.5	417.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030X5-625AXSP12	350.4	529.8	411.2	458.6	862.5	348.6	525.1	408.1	455.1	852.9	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X5-632AXSP12	329.8	503.5	389.4	434.6	827	328.2	499	386.4	431.9	817.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X9-525AXSP12	317.9	487.2	375.6	420.3	-	316.5	483	373.5	417.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL030X9-625AXSP12	350.4	529.8	411.2	458.6	862.5	348.6	525.1	408.1	455.1	852.9	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030X9-632AXSP12	329.8	503.5	389.4	434.6	827	328.2	499	386.4	431.9	817.5	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL030Y3-525AXSP16	320.9	487.9	377.3	421.6	-	319	483.7	374.6	418.5	-	316	26.7	4"	252	17.7	4"	379	37.5	4"
EAW-DD3351XL030Y3-625AXSP16	355.8	533.7	415.7	462.2	-	353.4	528.3	412	458.6	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL030Y3-632AXSP16	334.8	507.6	393.4	438.9	-	332.6	503	390.4	434.9	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL037M3-525AXSP12	341.7	525.4	404.6	452.6	-	340.8	520.9	401.8	449.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL037M3-625AXSP12	378.2	573.9	444.6	496.1	-	376.9	568.9	441.4	492.5	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL037M3-632AXSP12	355.2	543	418.9	468.7	-	353.5	538.9	416.5	465.1	884.4	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL037M4-525AXSP12	341.7	525.4	404.6	452.6	-	340.8	520.9	401.8	449.3	-	428	20.3	4"						

EAW-DD3351XL037X5-525AXSP12	334.1	512.3	394.9	441.5	-	332.8	508.1	392.2	439.1	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL037X5-625AXSP12	369.3	559.1	433.4	483.6	-	367.4	554.2	430.2	479.9	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL037X5-632AXSP12	346.7	530.2	409.4	457.2	871.9	345.1	525.6	406.4	453.8	862	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL037X9-525AXSP12	334.1	512.3	394.9	441.5	-	332.8	508.1	392.2	439.1	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL037X9-625AXSP12	369.3	559.1	433.4	483.6	-	367.4	554.2	430.2	479.9	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL037X9-632AXSP12	346.7	530.2	409.4	457.2	871.9	345.1	525.6	406.4	453.8	862	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL037Y3-525AXSP12	334.1	512.3	394.9	441.5	-	332.8	508.1	392.2	439.1	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL037Y3-625AXSP16	374.5	563.4	438.2	487.5	-	372	557.7	434.3	483.7	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL037Y3-632AXSP16	352	533.8	413.7	461.8	-	349.8	529.1	410	457.7	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL045M3-525AXSP12	360.2	554.4	426.2	477.7	-	359.2	550.3	424.3	474.8	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045M3-625AXSP12	399.1	606.7	469.3	524	-	397.4	601.8	466.2	520.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M3-632AXSP12	373.8	573.6	441.8	494.6	-	372.5	569.1	439.7	491.3	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M4-625AXSP12	360.2	554.4	426.2	477.7	-	359.2	550.3	424.3	474.8	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045M4-621AXSP08	377.2	586.1	449.7	504.5	966.9	378	583	448.7	503.2	958	789	14.6	4"	631	9.6	4"	947	20.5	4"
EAW-DD3351XL045M4-625AXSP12	399.1	606.7	469.3	524	-	397.4	601.8	466.2	520.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M4-632AXSP12	373.8	573.6	441.8	494.6	-	372.5	569.1	439.7	491.3	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M5-525AXSP12	360.2	554.4	426.2	477.7	-	359.2	550.3	424.3	474.8	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045M5-625AXSP12	399.1	606.7	469.3	524	-	397.4	601.8	466.2	520.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M5-632AXSP12	373.8	573.6	441.8	494.6	-	372.5	569.1	439.7	491.3	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M9-525AXSP12	360.2	554.4	426.2	477.7	-	359.2	550.3	424.3	474.8	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045M9-625AXSP12	399.1	606.7	469.3	524	-	397.4	601.8	466.2	520.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045M9-632AXSP12	373.8	573.6	441.8	494.6	-	372.5	569.1	439.7	491.3	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045N3-525AXSP12	348.7	535.8	412.3	461.3	-	347.2	531.1	409.4	458.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045N3-625AXSP12	386.8	586.6	454.8	506.9	-	384.8	582	451.3	503.6	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045N3-632AXSP12	362	553.8	427.7	477.8	-	360.2	549.5	424.4	474.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045N4-525AXSP12	348.7	535.8	412.3	461.3	-	347.2	531.1	409.4	458.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045N4-625AXSP12	386.8	586.6	454.8	506.9	-	384.8	582	451.3	503.6	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045N4-632AXSP12	362	553.8	427.7	477.8	-	360.2	549.5	424.4	474.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045N9-525AXSP12	348.7	535.8	412.3	461.3	-	347.2	531.1	409.4	458.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045N9-625AXSP12	386.8	586.6	454.8	506.9	-	384.8	582	451.3	503.6	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045N9-632AXSP12	362	553.8	427.7	477.8	-	360.2	549.5	424.4	474.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045Q3-525AXSP12	348.7	535.8	412.3	461.3	-	347.2	531.1	409.4	458.5	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045Q3-625AXSP12	386.8	586.6	454.8	506.9	-	384.8	582	451.3	503.6	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045Q3-632AXSP12	362	553.8	427.7	477.8	-	360.2	549.5	424.4	474.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045T3-525AXSP12	360.2	554.4	426.2	477.7	-	359.2	550.3	424.3	474.8	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045T3-625AXSP12	399.1	606.7	469.3	524	-	397.4	601.8	466.2	520.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045Y3-632AXSP12	373.8	573.6	441.8	494.6	-	372.5	569.1	439.7	491.3	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X3-525AXSP12	349.6	538.2	414.2	463.4	-	348.4	533.9	411.5	460.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045X3-625AXSP12	387.5	588.5	455.6	508.5	-	386.2	583.4	452.9	504.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X3-625AXSP16	393	593	460.7	513.4	-	391.1	587.1	456.7	508.8	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL045X3-632AXSP12	363.5	556.2	429.4	479.8	-	362	552.3	426.4	476.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X3-632AXSP16	368.6	560.9	434	484.8	-	366.4	556.1	430.3	480.6	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL045X4-525AXSP12	349.6	538.2	414.2	463.4	-	348.4	533.9	411.5	460.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045X4-625AXSP12	387.5	588.5	455.6	508.5	-	386.2	583.4	452.9	504.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X4-632AXSP12	363.5	556.2	429.4	479.8	-	362	552.3	426.4	476.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X5-525AXSP12	349.6	538.2	414.2	463.4	-	348.4	533.9	411.5	460.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045X5-625AXSP12	387.5	588.5	455.6	508.5	-	386.2	583.4	452.9	504.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X5-632AXSP12	363.5	556.2	429.4	479.8	-	362	552.3	426.4	476.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X9-525AXSP12	349.6	538.2	414.2	463.4	-	348.4	533.9	411.5	460.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045X9-625AXSP12	387.5	588.5	455.6	508.5	-	386.2	583.4	452.9	504.8	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045X9-632AXSP12	363.5	556.2	429.4	479.8	-	362	552.3	426.4	476.4	-	530	20.5	4"	424	13.6	4"	636	28.7	4"
EAW-DD3351XL045Y3-525AXSP12	349.6	538.2	414.2	463.4	-	348.4	533.9	411.5	460.3	-	428	20.3	4"	343	13.4	4"	514	28.4	4"
EAW-DD3351XL045Y3-625AXSP16	393	593	460.7	513.4	-	391.1	587.1	456.7	508.8	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3351XL045Y3-632AXSP16	368.6	560.9	434	484.8	-	366.4	556.1	430.3	480.6	-	394	26.9	4"	316	17.8	4"	473	37.6	4"
EAW-DD3352XL030M3-525AXSP06	658.8	1009.9	778.4	871.2	-	656.8	1000.8	773.8	864.5	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL030M3-625AXSP06	718.3	1087.2	843	940.4	-	714.7	1077.7	836.8	933.3	1751.9	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030M3-632AXSP06	674.2	1030.8	796.1	889	1694.8	670.8	1021.3	790	883.2	1676.8	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030M4-525AXSP06	658.8	1009.9	778.4	871.2	-	656.8	1000.8	773.8	864.5	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL030M4-625AXSP06	718.3	1087.2	843	940.4	-	714.7	1077.7	836.8	933.3	1751.9	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030M4-632AXSP06	674.2	1030.8	796.1	889	1694.8	670.8	1021.3	790	883.2	1676.8	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030M5-525AXSP06	658.8	1009.9	778.4	871.2	-	656.8	1000.8	773.8	864.5	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL030M5-625AXSP06	718.3	1087.2	843	940.4	-	714.7	1077.7	836.8	933.3	1751.9	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030M5-632AXSP06	674.2	1030.8	796.1	889	1694.8	670.8	1021.3	790	883.2	1676.8	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030M9-525AXSP06	658.8	1009.9	778.4	871.2	-	656.8	1000.8	773.8	864.5	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL030M9-625AXSP06	718.3	1087.2	843	940.4	-	714.7	1077.7	836.8	933.3	1751.9	1060	20.9	4"	848	13.8				

EAW-DD3352XL030X9-632AXSP06	655.7	1002.9	774.1	865.4	1645.7	653.6	994	769.5	858.9	1628.8	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL030Y3-525AXSP08	651.7	990.8	766.1	855.6	-	647.7	982.1	760.5	849.1	-	654	25.6	4"	523	16.9	4"	784	35.8	4"
EAW-DD3352XL030Y3-625AXSP08	708.6	1064.8	828	921.9	-	703.9	1054.1	821.8	913.7	-	789	26	4"	631	17.2	4"	947	36.4	4"
EAW-DD3352XL030Y3-632AXSP08	667.6	1011	783.3	874.1	-	663.3	1002	777.4	867.3	-	789	26	4"	631	17.2	4"	947	36.4	4"
EAW-DD3352XL037M3-525AXSP06	690	1059.9	815.6	913.4	-	688.2	1050.7	811.1	906.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037M3-625AXSP06	753.2	1141.9	884.2	986.9	-	749.6	1132.1	879.1	979.6	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037M3-632AXSP06	706	1081.6	834.1	933.3	-	703.9	1071.9	829.2	926.2	1762.1	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037M4-525AXSP06	690	1059.9	815.6	913.4	-	688.2	1050.7	811.1	906.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037M4-625AXSP06	753.2	1141.9	884.2	986.9	-	749.6	1132.1	879.1	979.6	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037M4-632AXSP06	706	1081.6	834.1	933.3	-	703.9	1071.9	829.2	926.2	1762.1	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037M9-525AXSP06	690	1059.9	815.6	913.4	-	688.2	1050.7	811.1	906.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037M9-625AXSP06	753.2	1141.9	884.2	986.9	-	749.6	1132.1	879.1	979.6	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037M9-632AXSP06	706	1081.6	834.1	933.3	-	703.9	1071.9	829.2	926.2	1762.1	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037N3-525AXSP06	680.9	1045.2	804.8	901	-	677.5	1035.3	799.6	893.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037N3-625AXSP06	744.5	1128.3	874	975.4	-	740.2	1117.5	868	967.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037N3-632AXSP06	696.9	1065.3	821.9	919.5	1755.5	693.2	1056.7	816.6	913.3	1736.3	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037N4-525AXSP06	680.9	1045.2	804.8	901	-	677.5	1035.3	799.6	893.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037N4-625AXSP06	744.5	1128.3	874	975.4	-	740.2	1117.5	868	967.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037N4-632AXSP06	696.9	1065.3	821.9	919.5	1755.5	693.2	1056.7	816.6	913.3	1736.3	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037N9-525AXSP06	680.9	1045.2	804.8	901	-	677.5	1035.3	799.6	893.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037N9-625AXSP06	744.5	1128.3	874	975.4	-	740.2	1117.5	868	967.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037N9-632AXSP06	696.9	1065.3	821.9	919.5	1755.5	693.2	1056.7	816.6	913.3	1736.3	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037Q3-525AXSP06	680.9	1045.2	804.8	901	-	677.5	1035.3	799.6	893.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037Q3-625AXSP06	744.5	1128.3	874	975.4	-	740.2	1117.5	868	967.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037Q3-632AXSP06	696.9	1065.3	821.9	919.5	1755.5	693.2	1056.7	816.6	913.3	1736.3	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037T3-525AXSP06	690	1059.9	815.6	913.4	-	688.2	1050.7	811.1	906.7	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037T3-625AXSP06	753.2	1141.9	884.2	986.9	-	749.6	1132.1	879.1	979.6	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037T3-632AXSP06	706	1081.6	834.1	933.3	-	703.9	1071.9	829.2	926.2	1762.1	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X3-525AXSP06	674.5	1033.4	797.2	891	-	671.8	1026.1	791.6	886	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037X3-525AXSP08	684.1	1042.2	805.7	900.3	-	680.1	1033.2	800	892.5	-	654	25.6	4"	523	16.9	4"	784	35.8	4"
EAW-DD3352XL037X3-625AXSP06	734.4	1112.6	862.1	961.9	-	730.8	1102.9	856.9	954.7	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X3-625AXSP08	745.8	1122.5	872.9	972.3	-	741	1112.6	866.3	963.6	-	789	26	4"	631	17.2	4"	947	36.4	4"
EAW-DD3352XL037X3-632AXSP06	689.1	1054.5	813.9	910.4	1734.9	687.1	1045.4	809.3	903.7	1717.5	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X3-632AXSP08	700.7	1064.7	823.7	919.7	-	696.5	1054	817.7	911.5	-	789	26	4"	631	17.2	4"	947	36.4	4"
EAW-DD3352XL037X4-525AXSP06	674.5	1033.4	797.2	891	-	671.8	1026.1	791.6	886	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037X4-625AXSP06	734.4	1112.6	862.1	961.9	-	730.8	1102.9	856.9	954.7	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X4-632AXSP06	689.1	1054.5	813.9	910.4	1734.9	687.1	1045.4	809.3	903.7	1717.5	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X5-525AXSP06	674.5	1033.4	797.2	891	-	671.8	1026.1	791.6	886	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037X5-625AXSP06	734.4	1112.6	862.1	961.9	-	730.8	1102.9	856.9	954.7	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X5-632AXSP06	689.1	1054.5	813.9	910.4	1734.9	687.1	1045.4	809.3	903.7	1717.5	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X9-525AXSP06	674.5	1033.4	797.2	891	-	671.8	1026.1	791.6	886	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL037X9-625AXSP06	734.4	1112.6	862.1	961.9	-	730.8	1102.9	856.9	954.7	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037X9-632AXSP06	689.1	1054.5	813.9	910.4	1734.9	687.1	1045.4	809.3	903.7	1717.5	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL037Y3-525AXSP08	684.1	1042.2	805.7	900.3	-	680.1	1033.2	800	892.5	-	654	25.6	4"	523	16.9	4"	784	35.8	4"
EAW-DD3352XL037Y3-625AXSP08	745.8	1122.5	872.9	972.3	-	741	1112.6	866.3	963.6	-	789	26	4"	631	17.2	4"	947	36.4	4"
EAW-DD3352XL037Y3-632AXSP08	700.7	1064.7	823.7	919.7	-	696.5	1054	817.7	911.5	-	789	26	4"	631	17.2	4"	947	36.4	4"
EAW-DD3352XL045M3-525AXSP06	727.6	1118.6	860.5	964.3	-	725.4	1110.1	856.7	958.3	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL045M3-625AXSP06	793.5	1207.1	934.6	1042.2	-	790.3	1197.4	928.5	1035.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M3-632AXSP06	744.1	1140.8	879.5	983.3	-	741.6	1131.9	874	978.3	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M4-525AXSP06	727.6	1118.6	860.5	964.3	-	725.4	1110.1	856.7	958.3	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL045M4-621AXSP06	788.2	1196.9	926.8	1034.4	-	785.9	1188.8	921.7	1028.6	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M4-625AXSP06	793.5	1207.1	934.6	1042.2	-	790.3	1197.4	928.5	1035.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M4-632AXSP06	744.1	1140.8	879.5	983.3	-	741.6	1131.9	874	978.3	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M5-525AXSP06	727.6	1118.6	860.5	964.3	-	725.4	1110.1	856.7	958.3	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL045M5-625AXSP06	793.5	1207.1	934.6	1042.2	-	790.3	1197.4	928.5	1035.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M5-632AXSP06	744.1	1140.8	879.5	983.3	-	741.6	1131.9	874	978.3	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M9-525AXSP06	727.6	1118.6	860.5	964.3	-	725.4	1110.1	856.7	958.3	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL045M9-625AXSP06	793.5	1207.1	934.6	1042.2	-	790.3	1197.4	928.5	1035.2	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045M9-632AXSP06	744.1	1140.8	879.5	983.3	-	741.6	1131.9	874	978.3	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045N3-525AXSP06	703	1080.8	832.5	931	-	701	1071.2	826.4	925.4	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL045N3-625AXSP06	769.2	1168.7	904.5	1009.7	-	766.3	1158.1	898.8	1001.8	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045N3-632AXSP06	719.4	1103.1	850.1	951.5	-	717.1	1093	844.9	944	-	1060	20.9	4"	848	13.8	4"	1271	29.3	4"
EAW-DD3352XL045N4-525AXSP06	703	1080.8	832.5	931	-	701	1071.2	826.4	925.4	-	879	20.1	4"	703	13.3	4"	1055	28.2	4"
EAW-DD3352XL045N4-625AXSP06	769.2	1168.7	904.5	1009.7	-	766.3	1158.1	898.8	1001.8	-	1060	20.9	4"						

EAW-DD3353XL030M3-625AXSP04	1071.4	1622.6	1257.6	1403.1	2647.9	1066.1	1608.4	1250.1	1392.6	2618.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M3-632AXSP04	1005.1	1537.7	1187.1	1327.8	2529.4	1000.2	1525.7	1179.7	1317.3	2502.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M4-525AXSP04	983.5	1506.4	1162.3	1301	-	979.1	1495	1153.7	1291	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030M4-625AXSP04	1071.4	1622.6	1257.6	1403.1	2647.9	1066.1	1608.4	1250.1	1392.6	2618.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M4-632AXSP04	1005.1	1537.7	1187.1	1327.8	2529.4	1000.2	1525.7	1179.7	1317.3	2502.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M5-525AXSP04	983.5	1506.4	1162.3	1301	-	979.1	1495	1153.7	1291	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030M5-625AXSP04	1071.4	1622.6	1257.6	1403.1	2647.9	1066.1	1608.4	1250.1	1392.6	2618.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M5-632AXSP04	1005.1	1537.7	1187.1	1327.8	2529.4	1000.2	1525.7	1179.7	1317.3	2502.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M9-525AXSP04	983.5	1506.4	1162.3	1301	-	979.1	1495	1153.7	1291	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030M9-625AXSP04	1071.4	1622.6	1257.6	1403.1	2647.9	1066.1	1608.4	1250.1	1392.6	2618.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030M9-632AXSP04	1005.1	1537.7	1187.1	1327.8	2529.4	1000.2	1525.7	1179.7	1317.3	2502.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N3-525AXSP04	949.3	1453.8	1121.4	1252.9	-	944.2	1439.7	1112.3	1244.2	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030N3-625AXSP04	1035.1	1566	1214.8	1354.9	2553.8	1030.1	1552.3	1206	1343.1	2522.4	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N3-632AXSP04	970.3	1482.4	1145.6	1280.8	2436.1	964.8	1469.6	1137.6	1269.8	2408.5	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N4-525AXSP04	949.3	1453.8	1121.4	1252.9	-	944.2	1439.7	1112.3	1244.2	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030N4-625AXSP04	1035.1	1566	1214.8	1354.9	2553.8	1030.1	1552.3	1206	1343.1	2522.4	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N4-632AXSP04	970.3	1482.4	1145.6	1280.8	2436.1	964.8	1469.6	1137.6	1269.8	2408.5	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N5-525AXSP04	949.3	1453.8	1121.4	1252.9	-	944.2	1439.7	1112.3	1244.2	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030N5-625AXSP04	1035.1	1566	1214.8	1354.9	2553.8	1030.1	1552.3	1206	1343.1	2522.4	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N5-632AXSP04	970.3	1482.4	1145.6	1280.8	2436.1	964.8	1469.6	1137.6	1269.8	2408.5	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N9-525AXSP04	949.3	1453.8	1121.4	1252.9	-	944.2	1439.7	1112.3	1244.2	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030N9-625AXSP04	1035.1	1566	1214.8	1354.9	2553.8	1030.1	1552.3	1206	1343.1	2522.4	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030N9-632AXSP04	970.3	1482.4	1145.6	1280.8	2436.1	964.8	1469.6	1137.6	1269.8	2408.5	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Q3-525AXSP04	949.3	1453.8	1121.4	1252.9	-	944.2	1439.7	1112.3	1244.2	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Q3-625AXSP04	1035.1	1566	1214.8	1354.9	2553.8	1030.1	1552.3	1206	1343.1	2522.4	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Q3-632AXSP04	970.3	1482.4	1145.6	1280.8	2436.1	964.8	1469.6	1137.6	1269.8	2408.5	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030T3-525AXSP04	983.5	1506.4	1162.3	1301	-	979.1	1495	1153.7	1291	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030T3-625AXSP04	1071.4	1622.6	1257.6	1403.1	2647.9	1066.1	1608.4	1250.1	1392.6	2618.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030T3-632AXSP04	1005.1	1537.7	1187.1	1327.8	2529.4	1000.2	1525.7	1179.7	1317.3	2502.6	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030X3-525AXSP04	958.2	1465.8	1130.3	1264.8	-	954	1455.1	1123.9	1255.4	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030X3-625AXSP04	1041.2	1575.4	1221.9	1363	2566.3	1036	1561.6	1214.6	1352.7	2540.9	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030X3-632AXSP06	1070.2	1603.2	1248.7	1390.2	-	1063	1587	1239.2	1377.6	-	1060	29.4	4"	848	19.4	4"	1271	41.3	4"
EAW-DD3353XL030X3-632AXSP04	979.1	1496.2	1156	1292.6	2459.3	974.5	1483	1147.5	1282.8	2434.1	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030X3-632AXSP06	1007.4	1524.7	1181.8	1318.6	-	1000.8	1508.9	1172.8	1306.5	-	1060	29.4	4"	848	19.4	4"	1271	41.3	4"
EAW-DD3353XL030X4-525AXSP04	958.2	1465.8	1130.3	1264.8	-	954	1455.1	1123.9	1255.4	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030X4-625AXSP04	1041.2	1575.4	1221.9	1363	2566.3	1036	1561.6	1214.6	1352.7	2540.9	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030X4-632AXSP04	979.1	1496.2	1156	1292.6	2459.3	974.5	1483	1147.5	1282.8	2434.1	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030X5-525AXSP04	958.2	1465.8	1130.3	1264.8	-	954	1455.1	1123.9	1255.4	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030X5-625AXSP04	1041.2	1575.4	1221.9	1363	2566.3	1036	1561.6	1214.6	1352.7	2540.9	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030X5-632AXSP04	979.1	1496.2	1156	1292.6	2459.3	974.5	1483	1147.5	1282.8	2434.1	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-525AXSP04	958.2	1465.8	1130.3	1264.8	-	954	1455.1	1123.9	1255.4	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-625AXSP06	1070.2	1603.2	1248.7	1390.2	-	1063	1587	1239.2	1377.6	-	1060	29.4	4"	848	19.4	4"	1271	41.3	4"
EAW-DD3353XL030Y3-632AXSP06	1007.4	1524.7	1181.8	1318.6	-	1000.8	1508.9	1172.8	1306.5	-	1060	29.4	4"	848	19.4	4"	1271	41.3	4"
EAW-DD3353XL030Y3-632AXSP04	1030	1580.7	1217.7	1363.9	-	1025.8	1569.4	1211.1	1354	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-632AXSP04	1123.3	1706.3	1320.8	1474.3	-	1118.1	1691.7	1313.2	1463.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1054.1	1613.3	1243.5	1391.7	-	1049.3	1601.3	1236.3	1383.2	2633	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1030	1580.7	1217.7	1363.9	-	1025.8	1569.4	1211.1	1354	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-632AXSP04	1123.3	1706.3	1320.8	1474.3	-	1118.1	1691.7	1313.2	1463.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1054.1	1613.3	1243.5	1391.7	-	1049.3	1601.3	1236.3	1383.2	2633	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1030	1580.7	1217.7	1363.9	-	1025.8	1569.4	1211.1	1354	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-632AXSP04	1123.3	1706.3	1320.8	1474.3	-	1118.1	1691.7	1313.2	1463.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1054.1	1613.3	1243.5	1391.7	-	1049.3	1601.3	1236.3	1383.2	2633	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1014.9	1558.9	1201.6	1343.5	-	1011.4	1546.4	1192.1	1334.6	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-632AXSP04	1110.4	1686	1305.6	1457.1	-	1104	1669.8	1296.6	1444.9	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1038.8	1591.4	1227.3	1373.2	2619.8	1033.5	1576.4	1219.4	1362.1	2591.3	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1014.9	1558.9	1201.6	1343.5	-	1011.4	1546.4	1192.1	1334.6	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-632AXSP04	1110.4	1686	1305.6	1457.1	-	1104	1669.8	1296.6	1444.9	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1038.8	1591.4	1227.3	1373.2	2619.8	1033.5	1576.4	1219.4	1362.1	2591.3	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1014.9	1558.9	1201.6	1343.5	-	1011.4	1546.4	1192.1	1334.6	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL030Y3-632AXSP04	1110.4	1686	1305.6	1457.1	-	1104	1669.8	1296.6	1444.9	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL030Y3-632AXSP04	1038.8	1591.4	1227.3	1373.2	2619.8	1033.5	1576.4	1219.4	1362.1	2591.3	1589	19	6"	1271	15.4				

EAW-DD3353XL045M5-632AXSP04	1109.1	1704	1311.1	1468.3	-	1105.4	1690.7	1305	1458.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045M9-525AXSP04	1084.2	1668.1	1284.6	1437.6	-	1081.1	1657.9	1277	1428.7	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045M9-625AXSP04	1183.4	1801.2	1394	1556.9	-	1180.4	1789.2	1386.8	1546.4	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045M9-632AXSP04	1109.1	1704	1311.1	1468.3	-	1105.4	1690.7	1305	1458.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N3-525AXSP04	1049.4	1612	1240.9	1390.2	-	1044.9	1600	1233.9	1379.8	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045N3-625AXSP04	1147.1	1744	1351	1508.3	-	1142.9	1730.5	1340.7	1496.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N3-632AXSP04	1074.1	1645.3	1269.3	1418.7	-	1069	1632.7	1259.8	1409.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N4-525AXSP04	1049.4	1612	1240.9	1390.2	-	1044.9	1600	1233.9	1379.8	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045N4-625AXSP04	1147.1	1744	1351	1508.3	-	1142.9	1730.5	1340.7	1496.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N4-632AXSP04	1074.1	1645.3	1269.3	1418.7	-	1069	1632.7	1259.8	1409.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N5-525AXSP04	1049.4	1612	1240.9	1390.2	-	1044.9	1600	1233.9	1379.8	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045N5-625AXSP04	1147.1	1744	1351	1508.3	-	1142.9	1730.5	1340.7	1496.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N5-632AXSP04	1074.1	1645.3	1269.3	1418.7	-	1069	1632.7	1259.8	1409.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N9-525AXSP04	1049.4	1612	1240.9	1390.2	-	1044.9	1600	1233.9	1379.8	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045N9-625AXSP04	1147.1	1744	1351	1508.3	-	1142.9	1730.5	1340.7	1496.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045N9-632AXSP04	1074.1	1645.3	1269.3	1418.7	-	1069	1632.7	1259.8	1409.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045Q3-525AXSP04	1049.4	1612	1240.9	1390.2	-	1044.9	1600	1233.9	1379.8	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045Q3-625AXSP04	1147.1	1744	1351	1508.3	-	1142.9	1730.5	1340.7	1496.6	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045Q3-632AXSP04	1074.1	1645.3	1269.3	1418.7	-	1069	1632.7	1259.8	1409.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045T3-525AXSP04	1084.2	1668.1	1284.6	1437.6	-	1081.1	1657.9	1277	1428.7	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045T3-625AXSP04	1183.4	1801.2	1394	1556.9	-	1180.4	1789.2	1386.8	1546.4	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045T3-632AXSP04	1109.1	1704	1311.1	1468.3	-	1105.4	1690.7	1305	1458.8	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X3-525AXSP04	1054	1619.3	1246.4	1396.5	-	1050.3	1608.5	1240.3	1387.1	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045X3-625AXSP04	1150.7	1749.5	1353.3	1511	-	1145.5	1734.6	1345.6	1500	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X3-632AXSP04	1078.4	1652.3	1274.5	1424.6	-	1074.2	1640.8	1265.9	1416.7	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X4-525AXSP04	1054	1619.3	1246.4	1396.5	-	1050.3	1608.5	1240.3	1387.1	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045X4-625AXSP04	1150.7	1749.5	1353.3	1511	-	1145.5	1734.6	1345.6	1500	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X4-632AXSP04	1078.4	1652.3	1274.5	1424.6	-	1074.2	1640.8	1265.9	1416.7	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X5-525AXSP04	1054	1619.3	1246.4	1396.5	-	1050.3	1608.5	1240.3	1387.1	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045X5-625AXSP04	1150.7	1749.5	1353.3	1511	-	1145.5	1734.6	1345.6	1500	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X5-632AXSP04	1078.4	1652.3	1274.5	1424.6	-	1074.2	1640.8	1265.9	1416.7	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X9-525AXSP04	1054	1619.3	1246.4	1396.5	-	1050.3	1608.5	1240.3	1387.1	-	1319	21.7	4"	1055	14.3	4"	1582	26.2	6"
EAW-DD3353XL045X9-625AXSP04	1150.7	1749.5	1353.3	1511	-	1145.5	1734.6	1345.6	1500	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045X9-632AXSP04	1078.4	1652.3	1274.5	1424.6	-	1074.2	1640.8	1265.9	1416.7	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045Y3-625AXSP04	1150.7	1749.5	1353.3	1511	-	1145.5	1734.6	1345.6	1500	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-DD3353XL045Y3-632AXSP04	1078.4	1652.3	1274.5	1424.6	-	1074.2	1640.8	1265.9	1416.7	-	1589	19	6"	1271	15.4	4"	1907	26.6	6"
EAW-FD1551PB8370C2-425AXSP16	37.7	60.3	45.6	51.5	102.1	38.1	60.4	45.9	51.8	102.2	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C2-432AXSP16	35.1	56.5	42.7	48.3	96.5	35.4	56.7	42.9	48.5	96.4	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C2-525AXSP16	41	64.9	49.3	55.7	108.7	41.5	65.1	49.7	56	108.8	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C2-532AXSP16	38.8	62.2	47	53.3	104.9	39.3	62.4	47.4	53.4	104.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C2-532AXSP16	43	67.4	51.4	57.9	111.6	43.5	67.7	51.8	58.3	111.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C2-632AXSP16	41.4	65.7	49.9	56.3	109.9	42	66	50.2	56.6	109.9	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C4-425AXSP16	37.7	60.3	45.6	51.5	102.1	38.1	60.4	45.9	51.8	102.2	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C4-432AXSP16	35.1	56.5	42.7	48.3	96.5	35.4	56.7	42.9	48.5	96.4	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C4-525AXSP16	41	64.9	49.3	55.7	108.7	41.5	65.1	49.7	56	108.8	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C4-532AXSP16	38.8	62.2	47	53.3	104.9	39.3	62.4	47.4	53.4	104.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C4-625AXSP16	43	67.4	51.4	57.9	111.6	43.5	67.7	51.8	58.3	111.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C4-632AXSP16	41.4	65.7	49.9	56.3	109.9	42	66	50.2	56.6	109.9	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C5-425AXSP16	37.7	60.3	45.6	51.5	102.1	38.1	60.4	45.9	51.8	102.2	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C5-432AXSP16	35.1	56.5	42.7	48.3	96.5	35.4	56.7	42.9	48.5	96.4	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C5-525AXSP16	41	64.9	49.3	55.7	108.7	41.5	65.1	49.7	56	108.8	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C5-532AXSP16	38.8	62.2	47	53.3	104.9	39.3	62.4	47.4	53.4	104.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C5-625AXSP16	43	67.4	51.4	57.9	111.6	43.5	67.7	51.8	58.3	111.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C5-632AXSP16	41.4	65.7	49.9	56.3	109.9	42	66	50.2	56.6	109.9	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C8-425AXSP16	37.7	60.3	45.6	51.5	102.1	38.1	60.4	45.9	51.8	102.2	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C8-432AXSP16	35.1	56.5	42.7	48.3	96.5	35.4	56.7	42.9	48.5	96.4	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370C8-525AXSP16	41	64.9	49.3	55.7	108.7	41.5	65.1	49.7	56	108.8	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C8-532AXSP16	38.8	62.2	47	53.3	104.9	39.3	62.4	47.4	53.4	104.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370C8-625AXSP16	43	67.4	51.4	57.9	111.6	43.5	67.7	51.8	58.3	111.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370C8-632AXSP16	41.4	65.7	49.9	56.3	109.9	42	66	50.2	56.6	109.9	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD1551PB8370K2-425AXSP16	36.8	58.9	44.6	50.4	99.7	37.2	59	44.8	50.6	99.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370K2-432AXSP16	34.2	55.1	41.5	47.1	93.8	34.5	55.2	41.7	47.3	93.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD1551PB8370K2-525AXSP16	40.5	64	48.7	54.9	107.1	40.9	64.1	49	55.2	107.1	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD1551PB8370K2-532AXSP16	38.1																		

EAW-FD15S1PB400C9-625AXSP16	43	67.4	51.4	57.9	111.6	43.5	67.7	51.8	58.3	111.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400C9-632AXSP16	41.4	65.7	49.9	56.3	109.9	42	66	50.2	56.6	109.9	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400K3-425AXSP16	36.8	58.9	44.6	50.4	99.7	37.2	59	44.8	50.6	99.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB400K3-432AXSP16	34.2	55.1	41.5	47.1	93.8	34.5	55.2	41.7	47.3	93.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB400K3-525AXSP16	40.5	64	48.7	54.9	107.1	40.9	64.1	49	55.2	107.1	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB400K3-532AXSP16	38.1	60.9	46.1	52.2	102.7	38.4	61	46.3	52.3	102.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB400K3-625AXSP16	42.8	67.3	51.3	57.7	111.2	43.2	67.3	51.5	57.9	111	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400K3-632AXSP16	40.9	64.9	49.3	55.6	108.6	41.4	65.1	49.5	55.8	108.3	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400K9-425AXSP16	36.8	58.9	44.6	50.4	99.7	37.2	59	44.8	50.6	99.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB400K9-432AXSP16	34.2	55.1	41.5	47.1	93.8	34.5	55.2	41.7	47.3	93.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB400K9-525AXSP16	40.5	64	48.7	54.9	107.1	40.9	64.1	49	55.2	107.1	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB400K9-532AXSP16	38.1	60.9	46.1	52.2	102.7	38.4	61	46.3	52.3	102.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB400K9-625AXSP16	42.8	67.3	51.3	57.7	111.2	43.2	67.3	51.5	57.9	111	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400K9-632AXSP16	40.9	64.9	49.3	55.6	108.6	41.4	65.1	49.5	55.8	108.3	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400R3-425AXSP16	37.2	59.5	45.1	50.9	100.8	37.6	59.7	45.4	51.1	100.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB400R3-432AXSP16	34.5	55.7	42	47.6	94.9	34.9	55.8	42.2	47.8	94.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB400R3-525AXSP16	40.8	64.7	49.1	55.5	108.3	41.2	64.8	49.5	55.7	108.1	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB400R3-532AXSP16	38.4	61.5	46.5	52.7	103.9	38.9	61.7	46.8	52.9	103.7	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB400R3-625AXSP16	43.2	67.9	51.8	58.2	112.3	43.7	68	52	58.5	112.1	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB400R3-632AXSP16	41.3	65.6	49.8	56.2	109.5	41.8	65.7	50	56.3	109.3	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550B3-425AXSP16	38.9	62.2	47.1	53.2	105.6	39.4	62.5	47.4	53.6	105.7	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550B3-432AXSP16	36.3	58.5	44.2	50	100	36.8	58.8	44.5	50.3	100.1	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550B3-525AXSP16	-	-	-	-	-	-	-	-	-	-	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550B3-532AXSP16	-	-	-	-	-	40.6	64.3	48.8	55.2	108.3	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550B3-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550B3-632AXSP16	-	-	-	-	-	-	-	-	-	-	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C2-425AXSP16	41.7	66.6	50.4	57	-	42.2	67	50.8	57.4	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C2-432AXSP16	38.7	62.3	46.9	53.2	106.7	39.1	62.5	47.3	53.5	106.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C2-525AXSP16	45.6	72.2	54.9	62	121.5	46.1	72.6	55.3	62.3	121.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C2-532AXSP16	42.9	68.7	52	58.9	116.4	43.5	69.1	52.5	59.2	116.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C2-632AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C3-425AXSP16	41.7	66.6	50.4	57	-	42.2	67	50.8	57.4	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C3-432AXSP16	38.7	62.3	46.9	53.2	106.7	39.1	62.5	47.3	53.5	106.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C3-525AXSP16	45.6	72.2	54.9	62	121.5	46.1	72.6	55.3	62.3	121.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C3-532AXSP16	42.9	68.7	52	58.9	116.4	43.5	69.1	52.5	59.2	116.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C3-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C3-632AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C4-425AXSP16	41.7	66.6	50.4	57	-	42.2	67	50.8	57.4	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C4-432AXSP16	38.7	62.3	46.9	53.2	106.7	39.1	62.5	47.3	53.5	106.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C4-525AXSP16	45.6	72.2	54.9	62	121.5	46.1	72.6	55.3	62.3	121.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C4-532AXSP16	42.9	68.7	52	58.9	116.4	43.5	69.1	52.5	59.2	116.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C4-632AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C5-425AXSP16	41.7	66.6	50.4	57	-	42.2	67	50.8	57.4	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C5-432AXSP16	38.7	62.3	46.9	53.2	106.7	39.1	62.5	47.3	53.5	106.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C5-525AXSP16	45.6	72.2	54.9	62	121.5	46.1	72.6	55.3	62.3	121.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C5-532AXSP16	42.9	68.7	52	58.9	116.4	43.5	69.1	52.5	59.2	116.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C5-632AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C8-425AXSP16	41.7	66.6	50.4	57	-	42.2	67	50.8	57.4	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C8-432AXSP16	38.7	62.3	46.9	53.2	106.7	39.1	62.5	47.3	53.5	106.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C8-525AXSP16	45.6	72.2	54.9	62	121.5	46.1	72.6	55.3	62.3	121.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C8-532AXSP16	42.9	68.7	52	58.9	116.4	43.5	69.1	52.5	59.2	116.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C8-632AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C9-425AXSP16	41.7	66.6	50.4	57	-	42.2	67	50.8	57.4	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C9-432AXSP16	38.7	62.3	46.9	53.2	106.7	39.1	62.5	47.3	53.5	106.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550C9-525AXSP16	45.6	72.2	54.9	62	121.5	46.1	72.6	55.3	62.3	121.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C9-532AXSP16	42.9	68.7	52	58.9	116.4	43.5	69.1	52.5	59.2	116.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550C9-625AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550C9-632AXSP16	-	-	-	-	-	46.6	73.4	55.8	63	122.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550K2-425AXSP16	40.1	64.1	48.6	54.9	109	40.6	64.3	48.8	55.1	108.9	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550K2-432AXSP16	37.1	59.8	45.2	51.1	102.2	37.5	60	45.4	51.4	102.2	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550K2-525AXSP16	44	69.8	53	59.9	117.2	44.5	70	53.4	60.1	117.1	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550K2-532AXSP16	41.4	66.3	50.1	56.7	112.1	41.9	66.4	50.5	57	112	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB550K2-625AXSP16	46.6	73.3	55.9	62.9	121.6	47.2	73.5	56.3	63.3	121.6	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550K2-632AXSP16	44.5	70.7	53.6	60.5	118.4	45	70.9	53.9	60.8	118.3	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB550K3-425AXSP16	40.1	64.1	48.6	54.9	109	40.6	64.3	48.8	55.1	108.9	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB550K3-432AXSP16	37.1	59.8	45.2	51.1	102.2	37.5	60	45.4	51.4	102.2	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-F																			

EAW-FD15S1PB750K2-432AXSP16	39	63	47.5	53.8	107.7	39.5	63.2	47.8	54	107.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K2-525AXSP16	46.1	73.2	55.7	62.8	123	46.7	73.4	56	63.1	123.2	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K2-532AXSP16	43.4	69.5	52.6	59.5	117.7	44	69.8	53	59.8	117.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K2-625AXSP16	48.8	76.7	58.5	66	127.6	49.4	77	58.9	66.3	127.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K2-632AXSP16	46.5	74	56.1	63.4	124.2	47.1	74.3	56.6	63.8	124.2	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K3-425AXSP16	42.2	67.4	51	57.6	-	42.7	67.7	51.4	58	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K3-432AXSP16	39	63	47.5	53.8	107.7	39.5	63.2	47.8	54	107.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K3-525AXSP16	46.1	73.2	55.7	62.8	123	46.7	73.4	56	63.1	123.2	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K3-532AXSP16	43.4	69.5	52.6	59.5	117.7	44	69.8	53	59.8	117.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K3-625AXSP16	48.8	76.7	58.5	66	127.6	49.4	77	58.9	66.3	127.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K3-632AXSP16	46.5	74	56.1	63.4	124.2	47.1	74.3	56.6	63.8	124.2	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K4-425AXSP16	42.2	67.4	51	57.6	-	42.7	67.7	51.4	58	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K4-432AXSP16	39	63	47.5	53.8	107.7	39.5	63.2	47.8	54	107.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K4-525AXSP16	46.1	73.2	55.7	62.8	123	46.7	73.4	56	63.1	123.2	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K4-532AXSP16	43.4	69.5	52.6	59.5	117.7	44	69.8	53	59.8	117.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K4-625AXSP16	48.8	76.7	58.5	66	127.6	49.4	77	58.9	66.3	127.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K4-632AXSP16	46.5	74	56.1	63.4	124.2	47.1	74.3	56.6	63.8	124.2	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K5-425AXSP16	42.2	67.4	51	57.6	-	42.7	67.7	51.4	58	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K5-432AXSP16	39	63	47.5	53.8	107.7	39.5	63.2	47.8	54	107.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K5-525AXSP16	46.1	73.2	55.7	62.8	123	46.7	73.4	56	63.1	123.2	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K5-532AXSP16	43.4	69.5	52.6	59.5	117.7	44	69.8	53	59.8	117.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K5-625AXSP16	48.8	76.7	58.5	66	127.6	49.4	77	58.9	66.3	127.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K5-632AXSP16	46.5	74	56.1	63.4	124.2	47.1	74.3	56.6	63.8	124.2	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K8-425AXSP16	42.2	67.4	51	57.6	-	42.7	67.7	51.4	58	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K8-432AXSP16	39	63	47.5	53.8	107.7	39.5	63.2	47.8	54	107.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K8-525AXSP16	46.1	73.2	55.7	62.8	123	46.7	73.4	56	63.1	123.2	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K8-532AXSP16	43.4	69.5	52.6	59.5	117.7	44	69.8	53	59.8	117.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K8-625AXSP16	48.8	76.7	58.5	66	127.6	49.4	77	58.9	66.3	127.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K8-632AXSP16	46.5	74	56.1	63.4	124.2	47.1	74.3	56.6	63.8	124.2	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K9-425AXSP16	42.2	67.4	51	57.6	-	42.7	67.7	51.4	58	-	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K9-432AXSP16	39	63	47.5	53.8	107.7	39.5	63.2	47.8	54	107.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750K9-525AXSP16	46.1	73.2	55.7	62.8	123	46.7	73.4	56	63.1	123.2	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K9-532AXSP16	43.4	69.5	52.6	59.5	117.7	44	69.8	53	59.8	117.9	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750K9-625AXSP16	48.8	76.7	58.5	66	127.6	49.4	77	58.9	66.3	127.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750K9-632AXSP16	46.5	74	56.1	63.4	124.2	47.1	74.3	56.6	63.8	124.2	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750R3-425AXSP16	41.4	66.1	50	56.6	112.4	41.8	66.4	50.4	56.9	112.6	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750R3-432AXSP16	38.3	61.7	46.6	52.8	105.7	38.7	62	46.9	53	105.8	68	18.9	1-1/2"	54	12.4	1-1/2"	81	22.1	2"
EAW-FD15S1PB750R3-525AXSP16	45.2	71.7	54.6	61.5	120.6	45.7	72	54.9	61.9	120.5	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750R3-532AXSP16	42.6	68.1	51.6	58.4	115.4	43.1	68.4	52	58.6	115.6	84	16.7	2"	68	14.2	1-1/2"	101	23.4	2"
EAW-FD15S1PB750R3-625AXSP16	47.8	75.1	57.3	64.6	124.9	48.4	75.4	57.8	65	125	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750R3-632AXSP16	45.7	72.6	55	62.2	121.7	46.2	72.9	55.4	62.5	121.7	101	17.8	2"	81	11.8	2"	122	20.7	3"
EAW-FD15S1PB750R3-632AXSP16	39.9	63.8	48.3	54.7	108.4	40.3	63.9	48.7	54.8	108.2	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C2-432AXSP16	37	59.7	45	51.1	102	37.4	59.8	45.2	51.2	101.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C2-525AXSP16	43.3	68.8	52.3	59.1	115.4	43.8	69	52.6	59.3	115.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C2-532AXSP16	40.8	65.5	49.5	56	110.7	41.3	65.6	49.8	56.2	110.5	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C2-625AXSP16	46.8	73.5	56	63.1	121.6	47.4	73.8	56.5	63.4	121.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C2-632AXSP16	45	71.4	54.1	61.2	119.2	45.4	71.5	54.5	61.3	119	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C4-425AXSP16	39.9	63.8	48.3	54.7	108.4	40.3	63.9	48.7	54.8	108.2	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C4-432AXSP16	37	59.7	45	51.1	102	37.4	59.8	45.2	51.2	101.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C4-525AXSP16	43.3	68.8	52.3	59.1	115.4	43.8	69	52.6	59.3	115.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C4-532AXSP16	40.8	65.5	49.5	56	110.7	41.3	65.6	49.8	56.2	110.5	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C4-625AXSP16	46.8	73.5	56	63.1	121.6	47.4	73.8	56.5	63.4	121.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C4-632AXSP16	45	71.4	54.1	61.2	119.2	45.4	71.5	54.5	61.3	119	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C5-425AXSP16	39.9	63.8	48.3	54.7	108.4	40.3	63.9	48.7	54.8	108.2	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C5-432AXSP16	37	59.7	45	51.1	102	37.4	59.8	45.2	51.2	101.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C5-525AXSP16	43.3	68.8	52.3	59.1	115.4	43.8	69	52.6	59.3	115.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C5-532AXSP16	40.8	65.5	49.5	56	110.7	41.3	65.6	49.8	56.2	110.5	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C5-625AXSP16	46.8	73.5	56	63.1	121.6	47.4	73.8	56.5	63.4	121.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C5-632AXSP16	45	71.4	54.1	61.2	119.2	45.4	71.5	54.5	61.3	119	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C8-425AXSP16	39.9	63.8	48.3	54.7	108.4	40.3	63.9	48.7	54.8	108.2	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C8-432AXSP16	37	59.7	45	51.1	102	37.4	59.8	45.2	51.2	101.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB370C8-525AXSP16	43.3	68.8	52.3	59.1	115.4	43.8	69	52.6	59.3	115.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C8-532AXSP16	40.8	65.5	49.5	56	110.7	41.3	65.6	49.8	56.2	110.5	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB370C8-625AXSP16	46.8	73.5	56	63.1	121.6	47.4	73.8	56.5	63.4	121.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB370C8-632AXSP16	45	71.4	54.1	61.2	119.2	45.4	71.5	54.5	61.3	119	113	18.8	2"	90	12.4	2"	135	20.9	3"

EAW-FD15S1ZB400C9-425AXSP16	39.9	63.8	48.3	54.7	108.4	40.3	63.9	48.7	54.8	108.2	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400C9-432AXSP16	37	59.7	45	51.1	102	37.4	59.8	45.2	51.2	101.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400C9-525AXSP16	43.3	68.8	52.3	59.1	115.4	43.8	69	52.6	59.3	115.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400C9-532AXSP16	40.8	65.5	49.5	56	110.7	41.3	65.6	49.8	56.2	110.5	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400C9-625AXSP16	46.8	73.5	56	63.1	121.6	47.4	73.8	56.5	63.4	121.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400C9-632AXSP16	45	71.4	54.1	61.2	119.2	45.4	71.5	54.5	61.3	119	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400K3-425AXSP16	38.8	62	47	53.1	105.2	39.1	62.1	47.2	53.2	104.8	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400K3-432AXSP16	35.9	57.9	43.6	49.5	98.6	36.2	57.9	43.8	49.6	98.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400K3-525AXSP16	42.3	67.2	51.1	57.7	112.6	42.8	67.2	51.3	57.8	112.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400K3-532AXSP16	39.8	63.8	48.2	54.5	107.7	40.1	63.8	48.4	54.7	107.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400K3-625AXSP16	46.1	72.4	55.2	62.1	119.8	46.5	72.5	55.5	62.3	119.4	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400K3-632AXSP16	44	69.8	52.9	59.8	116.6	44.4	69.8	53.1	59.9	116.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400K9-425AXSP16	38.8	62	47	53.1	105.2	39.1	62.1	47.2	53.2	104.8	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400K9-432AXSP16	35.9	57.9	43.6	49.5	98.6	36.2	57.9	43.8	49.6	98.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400K9-532AXSP16	42.3	67.2	51.1	57.7	112.6	42.8	67.2	51.3	57.8	112.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400K9-625AXSP16	39.8	63.8	48.2	54.5	107.7	40.1	63.8	48.4	54.7	107.3	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400K9-632AXSP16	46.1	72.4	55.2	62.1	119.8	46.5	72.5	55.5	62.3	119.4	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400K9-632AXSP16	44	69.8	52.9	59.8	116.6	44.4	69.8	53.1	59.9	116.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400R3-425AXSP16	39.3	62.8	47.6	53.7	106.3	39.6	62.8	47.8	53.9	106.2	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400R3-432AXSP16	36.3	58.6	44.2	50.1	100	36.7	58.7	44.4	50.3	99.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB400R3-525AXSP16	42.9	68	51.7	58.4	113.9	43.3	68	51.9	58.5	113.6	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400R3-532AXSP16	40.2	64.5	48.7	55.1	108.8	40.6	64.6	49	55.3	108.6	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB400R3-625AXSP16	46.6	73.2	55.8	62.8	121	47	73.2	56	63	120.7	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB400R3-632AXSP16	44.4	70.5	53.6	60.4	117.9	44.9	70.6	53.8	60.6	117.5	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550B3-425AXSP16	41.5	66.4	50.3	56.8	112.8	42	66.6	50.6	57.1	112.7	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550B3-432AXSP16	38.6	62.2	46.9	53.2	106.3	39	62.4	47.2	53.4	106.3	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550B3-525AXSP16	44.8	71.1	54	61	119.4	45.4	71.5	54.5	61.4	119.5	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550B3-532AXSP16	42.4	67.9	51.3	58.1	114.9	42.9	68.2	51.8	58.5	115	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550B3-625AXSP16	-	-	-	-	-	-	-	-	-	-	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550B3-632AXSP16	-	-	-	-	-	47	74	56.3	63.5	123.4	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C2-425AXSP16	44.3	70.8	53.6	60.6	120.5	44.7	71.1	53.9	60.9	120.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C2-432AXSP16	40.9	65.9	49.7	56.3	112.7	41.3	66	50	56.5	112.6	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C2-525AXSP16	48.2	76.6	58.3	65.7	129	48.8	76.9	58.6	66	129	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C2-532AXSP16	45.2	72.5	54.8	62.1	123	45.7	72.7	55.2	62.4	122.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C3-625AXSP16	52.4	82.3	62.8	70.7	136.8	53	82.6	63.3	71.1	136.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C3-632AXSP16	50	79.4	60.3	68.1	133.3	50.6	79.7	60.7	68.4	133.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C3-425AXSP16	44.3	70.8	53.6	60.6	120.5	44.7	71.1	53.9	60.9	120.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C3-432AXSP16	40.9	65.9	49.7	56.3	112.7	41.3	66	50	56.5	112.6	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C3-525AXSP16	48.2	76.6	58.3	65.7	129	48.8	76.9	58.6	66	129	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C3-632AXSP16	45.2	72.5	54.8	62.1	123	45.7	72.7	55.2	62.4	122.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C4-625AXSP16	52.4	82.3	62.8	70.7	136.8	53	82.6	63.3	71.1	136.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C4-632AXSP16	50	79.4	60.3	68.1	133.3	50.6	79.7	60.7	68.4	133.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C4-425AXSP16	44.3	70.8	53.6	60.6	120.5	44.7	71.1	53.9	60.9	120.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C4-432AXSP16	40.9	65.9	49.7	56.3	112.7	41.3	66	50	56.5	112.6	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C4-525AXSP16	48.2	76.6	58.3	65.7	129	48.8	76.9	58.6	66	129	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C4-532AXSP16	45.2	72.5	54.8	62.1	123	45.7	72.7	55.2	62.4	122.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C4-625AXSP16	52.4	82.3	62.8	70.7	136.8	53	82.6	63.3	71.1	136.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C4-632AXSP16	50	79.4	60.3	68.1	133.3	50.6	79.7	60.7	68.4	133.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C5-425AXSP16	44.3	70.8	53.6	60.6	120.5	44.7	71.1	53.9	60.9	120.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C5-432AXSP16	40.9	65.9	49.7	56.3	112.7	41.3	66	50	56.5	112.6	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C5-525AXSP16	48.2	76.6	58.3	65.7	129	48.8	76.9	58.6	66	129	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C5-632AXSP16	45.2	72.5	54.8	62.1	123	45.7	72.7	55.2	62.4	122.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C5-625AXSP16	52.4	82.3	62.8	70.7	136.8	53	82.6	63.3	71.1	136.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C5-632AXSP16	50	79.4	60.3	68.1	133.3	50.6	79.7	60.7	68.4	133.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C8-425AXSP16	44.3	70.8	53.6	60.6	120.5	44.7	71.1	53.9	60.9	120.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C8-432AXSP16	40.9	65.9	49.7	56.3	112.7	41.3	66	50	56.5	112.6	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C8-525AXSP16	48.2	76.6	58.3	65.7	129	48.8	76.9	58.6	66	129	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C8-532AXSP16	45.2	72.5	54.8	62.1	123	45.7	72.7	55.2	62.4	122.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C8-625AXSP16	52.4	82.3	62.8	70.7	136.8	53	82.6	63.3	71.1	136.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C8-632AXSP16	50	79.4	60.3	68.1	133.3	50.6	79.7	60.7	68.4	133.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550C9-425AXSP16	44.3	70.8	53.6	60.6	120.5	44.7	71.1	53.9	60.9	120.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C9-432AXSP16	40.9	65.9	49.7	56.3	112.7	41.3	66	50	56.5	112.6	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550C9-525AXSP16	48.2	76.6	58.3	65.7	129	48.8	76.9	58.6	66	129	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C9-632AXSP16	45.2	72.5	54.8	62.1	123	45.7	72.7	55.2	62.4	122.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550C9-625AXSP16	52.4	82.3	62.8	70.7	136.8	53	82.6	63.3	71.1	136.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB5																			

EAW-FD15S1ZB550K9-632AXSP16	48	76.4	57.9	65.4	127.9	48.6	76.5	58.2	65.6	127.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550R3-425AXSP16	43.2	69.1	52.3	59.1	117.5	43.6	69.3	52.6	59.4	117.4	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550R3-432AXSP16	39.9	64.4	48.6	55	110.1	40.3	64.5	48.8	55.2	110	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB550R3-525AXSP16	47.2	75	57	64.3	126.1	47.7	75.1	57.3	64.5	125.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550R3-532AXSP16	44.2	70.9	53.6	60.7	120.1	44.7	71.1	53.9	60.9	119.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB550R3-625AXSP16	51.4	80.8	61.7	69.4	134.1	52	81	62	69.7	134	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB550R3-632AXSP16	48.9	77.8	59.1	66.6	130.3	49.4	77.9	59.4	66.9	130.1	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K2-425AXSP16	44.8	71.6	54.2	61.2	122	45.3	71.8	54.5	61.6	122	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K2-432AXSP16	41.3	66.7	50.3	57	114.3	41.8	66.9	50.6	57.2	114.1	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K2-525AXSP16	48.8	77.5	59	66.4	130.6	49.4	77.9	59.3	66.8	130.7	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K2-532AXSP16	45.8	73.3	55.5	62.8	124.5	46.2	73.6	55.9	63.1	124.4	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K2-625AXSP16	53.1	83.5	63.6	71.7	138.8	53.6	83.7	64.1	72	138.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K2-632AXSP16	50.6	80.4	61	68.9	134.8	51.1	80.6	61.4	69.3	134.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K3-425AXSP16	44.8	71.6	54.2	61.2	122	45.3	71.8	54.5	61.6	122	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K3-432AXSP16	41.3	66.7	50.3	57	114.3	41.8	66.9	50.6	57.2	114.1	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K3-525AXSP16	48.8	77.5	59	66.4	130.6	49.4	77.9	59.3	66.8	130.7	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K3-532AXSP16	45.8	73.3	55.5	62.8	124.5	46.2	73.6	55.9	63.1	124.4	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K3-625AXSP16	53.1	83.5	63.6	71.7	138.8	53.6	83.7	64.1	72	138.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K3-632AXSP16	50.6	80.4	61	68.9	134.8	51.1	80.6	61.4	69.3	134.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K4-425AXSP16	44.8	71.6	54.2	61.2	122	45.3	71.8	54.5	61.6	122	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K4-432AXSP16	41.3	66.7	50.3	57	114.3	41.8	66.9	50.6	57.2	114.1	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K4-525AXSP16	48.8	77.5	59	66.4	130.6	49.4	77.9	59.3	66.8	130.7	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K4-532AXSP16	45.8	73.3	55.5	62.8	124.5	46.2	73.6	55.9	63.1	124.4	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K5-425AXSP16	53.1	83.5	63.6	71.7	138.8	53.6	83.7	64.1	72	138.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K5-632AXSP16	50.6	80.4	61	68.9	134.8	51.1	80.6	61.4	69.3	134.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K5-632AXSP16	44.8	71.6	54.2	61.2	122	45.3	71.8	54.5	61.6	122	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K4-432AXSP16	41.3	66.7	50.3	57	114.3	41.8	66.9	50.6	57.2	114.1	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K4-525AXSP16	48.8	77.5	59	66.4	130.6	49.4	77.9	59.3	66.8	130.7	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K5-532AXSP16	45.8	73.3	55.5	62.8	124.5	46.2	73.6	55.9	63.1	124.4	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K5-625AXSP16	53.1	83.5	63.6	71.7	138.8	53.6	83.7	64.1	72	138.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K5-632AXSP16	50.6	80.4	61	68.9	134.8	51.1	80.6	61.4	69.3	134.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K8-425AXSP16	44.8	71.6	54.2	61.2	122	45.3	71.8	54.5	61.6	122	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K8-432AXSP16	41.3	66.7	50.3	57	114.3	41.8	66.9	50.6	57.2	114.1	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K8-525AXSP16	48.8	77.5	59	66.4	130.6	49.4	77.9	59.3	66.8	130.7	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K8-532AXSP16	45.8	73.3	55.5	62.8	124.5	46.2	73.6	55.9	63.1	124.4	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K8-625AXSP16	53.1	83.5	63.6	71.7	138.8	53.6	83.7	64.1	72	138.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K8-632AXSP16	50.6	80.4	61	68.9	134.8	51.1	80.6	61.4	69.3	134.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K9-425AXSP16	44.8	71.6	54.2	61.2	122	45.3	71.8	54.5	61.6	122	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K9-432AXSP16	41.3	66.7	50.3	57	114.3	41.8	66.9	50.6	57.2	114.1	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750K9-625AXSP16	48.8	77.5	59	66.4	130.6	49.4	77.9	59.3	66.8	130.7	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K9-632AXSP16	45.8	73.3	55.5	62.8	124.5	46.2	73.6	55.9	63.1	124.4	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750K9-632AXSP16	53.1	83.5	63.6	71.7	138.8	53.6	83.7	64.1	72	138.6	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750K9-632AXSP16	50.6	80.4	61	68.9	134.8	51.1	80.6	61.4	69.3	134.8	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750R3-425AXSP16	43.9	70.2	53.1	60.1	119.5	44.4	70.4	53.4	60.3	119.5	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750R3-432AXSP16	40.5	65.4	49.4	55.9	111.9	41	65.6	49.6	56.1	111.9	73	16.1	2"	59	13.1	1-1/2"	88	22.5	2"
EAW-FD15S1ZB750R3-525AXSP16	47.8	76	57.7	65.1	127.8	48.3	76.1	58	65.5	127.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750R3-532AXSP16	44.8	71.9	54.4	61.6	122	45.3	72.1	54.7	61.8	121.9	90	17.1	2"	72	11.3	2"	108	24.1	2"
EAW-FD15S1ZB750R3-625AXSP16	52	81.6	62.3	70.2	135.7	52.5	81.9	62.7	70.5	135.5	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZB750R3-632AXSP16	49.5	78.8	59.8	67.4	132	50.1	79	60.1	67.8	131.9	113	18.8	2"	90	12.4	2"	135	20.9	3"
EAW-FD15S1ZK370C2-425AXSP16	43.5	68.9	52.4	59	116.3	43.7	68.8	52.5	59.1	116	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK370C2-432AXSP16	40.2	64.2	48.7	55	109.2	40.5	64.3	48.8	55.1	108.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK370C2-525AXSP16	47.4	74.5	56.9	64.1	124.4	47.8	74.6	57.1	64.2	124	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK370C2-532AXSP16	44.6	70.8	53.8	60.8	119	44.9	70.8	54	60.8	118.8	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK370C2-625AXSP16	51.4	79.9	61.3	68.8	131.7	51.8	79.9	61.5	68.9	131.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK370C2-632AXSP16	49.2	77.4	59	66.5	128.7	49.6	77.4	59.2	66.5	128.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK370C4-425AXSP16	43.5	68.9	52.4	59	116.3	43.7	68.8	52.5	59.1	116	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK370C4-432AXSP16	40.2	64.2	48.7	55	109.2	40.5	64.3	48.8	55.1	108.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK370C4-525AXSP16	47.4	74.5	56.9	64.1	124.4	47.8	74.6	57.1	64.2	124	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK370C4-532AXSP16	44.6	70.8	53.8	60.8	119	44.9	70.8	54	60.8	118.8	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK370C4-625AXSP16	51.4	79.9	61.3	68.8	131.7	51.8	79.9	61.5	68.9	131.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK370C4-632AXSP16	49.2	77.4	59	66.5	128.7	49.6	77.4	59.2	66.5	128.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK370C5-425AXSP16	43.5	68.9	52.4	59	116.3	43.7	68.8	52.5	59.1	116	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK370C5-432AXSP16	40.2	64.2	48.7	55	109.2	40.5	64.3	48.8	55.1	108.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK370C5-525AXSP16	47.4	74.5	56.9	64.1	124.4	47.8	74.6	57.1	64.2	124	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK370C5-532AXSP16	44.6	70.8	53.8	60.8	119	44.9	70.8	54	60.8	118.8	90	18.3	2"	72					

EAW-FD15S1ZK400B3-625AXSP16	49.3	76.6	58.7	65.9	125.8	49.7	76.6	58.9	66.1	125.5	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400B3-632AXSP16	47.4	74.5	56.8	63.9	123.6	47.8	74.5	57	64.1	123.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400C3-425AXSP16	43.5	68.9	52.4	59	116.3	43.7	68.8	52.5	59.1	116	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400C3-432AXSP16	40.2	64.2	48.7	55	109.2	40.5	64.3	48.8	55.1	108.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400C3-525AXSP16	47.4	74.5	56.9	64.1	124.4	47.8	74.6	57.1	64.2	124	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400C3-532AXSP16	44.6	70.8	53.8	60.8	119	44.9	70.8	54	60.8	118.8	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400C3-625AXSP16	51.4	79.9	61.3	68.8	131.7	51.8	79.9	61.5	68.9	131.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400C3-632AXSP16	49.2	77.4	59	66.5	128.7	49.6	77.4	59.2	66.5	128.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400C9-425AXSP16	43.5	68.9	52.4	59	116.3	43.7	68.8	52.5	59.1	116	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400C9-432AXSP16	40.2	64.2	48.7	55	109.2	40.5	64.3	48.8	55.1	108.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400C9-525AXSP16	47.4	74.5	56.9	64.1	124.4	47.8	74.6	57.1	64.2	124	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400C9-532AXSP16	44.6	70.8	53.8	60.8	119	44.9	70.8	54	60.8	118.8	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400C9-625AXSP16	51.4	79.9	61.3	68.8	131.7	51.8	79.9	61.5	68.9	131.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400C9-632AXSP16	49.2	77.4	59	66.5	128.7	49.6	77.4	59.2	66.5	128.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400K3-425AXSP16	42.1	66.6	50.7	57.1	112.5	42.3	66.6	50.7	57.2	111.9	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400K3-432AXSP16	38.9	62.1	47.1	53.2	105.6	39.1	62.1	47.2	53.2	105.1	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400K3-525AXSP16	46	72.3	55.2	62.1	120.7	46.4	72.3	55.3	62.2	120.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400K3-532AXSP16	43.3	68.5	52.1	58.9	115.3	43.5	68.5	52.1	58.9	114.7	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400K3-625AXSP16	50.2	77.9	59.8	67.1	128.3	50.5	77.9	59.8	67.1	127.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400K3-632AXSP16	47.8	75.2	57.3	64.5	124.8	48.1	75.1	57.4	64.5	124.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400K9-425AXSP16	42.1	66.6	50.7	57.1	112.5	42.3	66.6	50.7	57.2	111.9	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400K9-432AXSP16	38.9	62.1	47.1	53.2	105.6	39.1	62.1	47.2	53.2	105.1	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400K9-525AXSP16	46	72.3	55.2	62.1	120.7	46.4	72.3	55.3	62.2	120.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400K9-532AXSP16	43.3	68.5	52.1	58.9	115.3	43.5	68.5	52.1	58.9	114.7	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400K9-625AXSP16	50.2	77.9	59.8	67.1	128.3	50.5	77.9	59.8	67.1	127.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400K9-632AXSP16	47.8	75.2	57.3	64.5	124.8	48.1	75.1	57.4	64.5	124.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400R3-425AXSP16	42.7	67.6	51.4	57.9	114	42.9	67.5	51.5	57.9	113.5	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400R3-432AXSP16	39.4	63.1	47.7	54	107	39.7	62.9	47.8	54	106.6	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK400R3-525AXSP16	46.6	73.2	55.9	62.9	122.3	47	73.2	56	62.9	121.8	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400R3-532AXSP16	43.8	69.4	52.8	59.6	116.7	44.1	69.4	52.8	59.7	116.4	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK400R3-625AXSP16	50.8	78.9	60.5	67.9	129.9	51.1	78.8	60.6	68	129.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK400R3-632AXSP16	48.4	76.1	58	65.4	126.4	48.7	76	58.2	65.3	125.8	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550B3-425AXSP16	45.5	72	54.7	61.8	121.9	45.8	72.2	54.9	61.9	121.7	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550B3-432AXSP16	42.2	67.4	51	57.6	114.7	42.5	67.5	51.2	57.8	114.5	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550B3-525AXSP16	49.4	77.5	59.3	66.7	129.8	49.8	77.7	59.5	66.8	129.5	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550B3-532AXSP16	46.5	73.8	56.1	63.4	124.4	46.9	74	56.4	63.5	124.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550B3-625AXSP16	53.2	82.8	63.5	71.3	136.6	53.8	83	63.9	71.5	136.5	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550B3-632AXSP16	51.2	80.5	61.3	69.2	133.9	51.6	80.6	61.7	69.3	133.8	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C2-425AXSP16	48.3	76.6	58.1	65.6	-	48.7	76.6	58.2	65.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C2-432AXSP16	44.5	71.1	53.8	60.8	121.2	44.8	71.1	54	60.9	120.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C2-525AXSP16	52.8	83.2	63.4	71.4	139.4	53.3	83.3	63.7	71.6	139.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C2-532AXSP16	49.5	78.5	59.8	67.3	132.7	49.8	78.6	59.9	67.5	132.3	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C2-625AXSP16	57.6	89.7	68.7	77.2	148.3	58.1	89.8	69.1	77.4	148.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C2-632AXSP16	54.9	86.4	65.8	74.2	144.1	55.3	86.4	66.1	74.4	143.8	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C3-425AXSP16	48.3	76.6	58.1	65.6	-	48.7	76.6	58.2	65.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C3-432AXSP16	44.5	71.1	53.8	60.8	121.2	44.8	71.1	54	60.9	120.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C3-525AXSP16	52.8	83.2	63.4	71.4	139.4	53.3	83.3	63.7	71.6	139.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C3-532AXSP16	49.5	78.5	59.8	67.3	132.7	49.8	78.6	59.9	67.5	132.3	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C3-625AXSP16	57.6	89.7	68.7	77.2	148.3	58.1	89.8	69.1	77.4	148.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C3-632AXSP16	54.9	86.4	65.8	74.2	144.1	55.3	86.4	66.1	74.4	143.8	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C4-425AXSP16	48.3	76.6	58.1	65.6	-	48.7	76.6	58.2	65.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C4-432AXSP16	44.5	71.1	53.8	60.8	121.2	44.8	71.1	54	60.9	120.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C4-525AXSP16	52.8	83.2	63.4	71.4	139.4	53.3	83.3	63.7	71.6	139.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C4-532AXSP16	49.5	78.5	59.8	67.3	132.7	49.8	78.6	59.9	67.5	132.3	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C4-625AXSP16	57.6	89.7	68.7	77.2	148.3	58.1	89.8	69.1	77.4	148.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C4-632AXSP16	54.9	86.4	65.8	74.2	144.1	55.3	86.4	66.1	74.4	143.8	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C5-425AXSP16	48.3	76.6	58.1	65.6	-	48.7	76.6	58.2	65.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C5-432AXSP16	44.5	71.1	53.8	60.8	121.2	44.8	71.1	54	60.9	120.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C5-525AXSP16	52.8	83.2	63.4	71.4	139.4	53.3	83.3	63.7	71.6	139.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C5-532AXSP16	49.5	78.5	59.8	67.3	132.7	49.8	78.6	59.9	67.5	132.3	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550C5-625AXSP16	57.6	89.7	68.7	77.2	148.3	58.1	89.8	69.1	77.4	148.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C5-632AXSP16	54.9	86.4	65.8	74.2	144.1	55.3	86.4	66.1	74.4	143.8	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550C8-425AXSP16	48.3	76.6	58.1	65.6	-	48.7	76.6	58.2	65.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C8-432AXSP16	44.5	71.1	53.8	60.8	121.2	44.8	71.1	54	60.9	120.8	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550C8-525AXSP16	52.8	83.2	63.4	71.4	139.4	53.3	83.3	63.7	71.6	139.2	90	18.3	2"	72	12	2"	108	25.7	2"

EAW-FD15S1ZK550K8-532AXSP16	47.3	75.2	57.1	64.4	126.8	47.7	75.2	57.3	64.6	126.4	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550K8-625AXSP16	55.2	85.8	65.8	74	141.7	55.5	85.8	66	74	141.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550K8-632AXSP16	52.4	82.6	62.9	71	137.6	52.9	82.6	63.1	71	137.1	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550K9-425AXSP16	46.2	73.1	55.5	62.7	-	46.5	73.2	55.7	62.8	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550K9-432AXSP16	42.6	68.1	51.5	58.3	115.9	42.9	68.1	51.7	58.3	115.5	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550K9-525AXSP16	50.5	79.5	60.7	68.3	132.9	50.9	79.5	60.8	68.4	132.7	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550K9-532AXSP16	47.3	75.2	57.1	64.4	126.8	47.7	75.2	57.3	64.6	126.4	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550K9-625AXSP16	55.2	85.8	65.8	74	141.7	55.5	85.8	66	74	141.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550K9-632AXSP16	52.4	82.6	62.9	71	137.6	52.9	82.6	63.1	71	137.1	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550R3-425AXSP16	47.1	74.7	56.7	63.9	-	47.5	74.7	56.9	64.1	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550R3-432AXSP16	43.5	69.5	52.5	59.4	118.4	43.8	69.5	52.7	59.6	118	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK550R3-525AXSP16	51.5	81.1	61.8	69.7	135.8	51.9	81.2	62.1	69.7	135.5	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550R3-532AXSP16	48.3	76.6	58.3	65.7	129.3	48.6	76.7	58.5	65.9	129	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK550R3-625AXSP16	56.2	87.6	67.2	75.5	144.9	56.7	87.6	67.4	75.6	144.3	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK550R3-632AXSP16	53.5	84.2	64.2	72.4	140.5	53.9	84.2	64.4	72.5	140.1	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750C4-425AXSP16	50.3	80	60.6	68.4	-	50.8	80.2	60.9	68.6	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750C4-432AXSP16	46.5	74.4	56.2	63.6	-	46.9	74.5	56.5	63.8	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750C4-525AXSP16	55	86.5	65.9	74.3	145.2	55.5	86.7	66.3	74.6	145.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750C4-532AXSP16	51.5	81.9	62.2	70.1	138.4	52	82	62.5	70.5	138.3	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750C4-625AXSP16	57	89.8	68.4	77.1	150	57.5	89.9	68.8	77.4	149.9	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750C4-632AXSP16	50.3	80	60.6	68.4	-	50.8	80.2	60.9	68.6	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750C5-425AXSP16	46.5	74.4	56.2	63.6	-	46.9	74.5	56.5	63.8	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750C5-525AXSP16	55	86.5	65.9	74.3	145.2	55.5	86.7	66.3	74.6	145.2	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750C5-532AXSP16	51.5	81.9	62.2	70.1	138.4	52	82	62.5	70.5	138.3	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750C5-625AXSP16	57	89.8	68.4	77.1	150	57.5	89.9	68.8	77.4	149.9	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K2-425AXSP16	48.9	77.6	58.9	66.4	-	49.3	77.7	59.1	66.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K2-432AXSP16	45.2	72.2	54.7	61.8	-	45.5	72.3	54.8	62	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K2-525AXSP16	53.5	84.1	64.2	72.3	141.2	54	84.3	64.4	72.5	141	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K2-532AXSP16	50.1	79.6	60.4	68.2	134.3	50.5	79.6	60.7	68.3	134.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K2-625AXSP16	58.3	90.7	69.6	78.2	150.3	58.8	90.9	69.9	78.4	150.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K2-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K3-425AXSP16	48.9	77.6	58.9	66.4	-	49.3	77.7	59.1	66.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K3-432AXSP16	45.2	72.2	54.7	61.8	-	45.5	72.3	54.8	62	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K3-525AXSP16	53.5	84.1	64.2	72.3	141.2	54	84.3	64.4	72.5	141	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K3-532AXSP16	50.1	79.6	60.4	68.2	134.3	50.5	79.6	60.7	68.3	134.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K3-625AXSP16	58.3	90.7	69.6	78.2	150.3	58.8	90.9	69.9	78.4	150.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K3-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K4-425AXSP16	48.9	77.6	58.9	66.4	-	49.3	77.7	59.1	66.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K4-432AXSP16	45.2	72.2	54.7	61.8	-	45.5	72.3	54.8	62	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K4-525AXSP16	53.5	84.1	64.2	72.3	141.2	54	84.3	64.4	72.5	141	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K4-532AXSP16	50.1	79.6	60.4	68.2	134.3	50.5	79.6	60.7	68.3	134.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K4-625AXSP16	58.3	90.7	69.6	78.2	150.3	58.8	90.9	69.9	78.4	150.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K4-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K5-425AXSP16	48.9	77.6	58.9	66.4	-	49.3	77.7	59.1	66.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K5-432AXSP16	45.2	72.2	54.7	61.8	-	45.5	72.3	54.8	62	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K5-525AXSP16	53.5	84.1	64.2	72.3	141.2	54	84.3	64.4	72.5	141	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K5-532AXSP16	50.1	79.6	60.4	68.2	134.3	50.5	79.6	60.7	68.3	134.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K5-625AXSP16	58.3	90.7	69.6	78.2	150.3	58.8	90.9	69.9	78.4	150.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K5-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K8-425AXSP16	48.9	77.6	58.9	66.4	-	49.3	77.7	59.1	66.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K8-432AXSP16	45.2	72.2	54.7	61.8	-	45.5	72.3	54.8	62	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K8-525AXSP16	53.5	84.1	64.2	72.3	141.2	54	84.3	64.4	72.5	141	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K8-532AXSP16	50.1	79.6	60.4	68.2	134.3	50.5	79.6	60.7	68.3	134.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K8-625AXSP16	58.3	90.7	69.6	78.2	150.3	58.8	90.9	69.9	78.4	150.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K8-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-425AXSP16	48.9	77.6	58.9	66.4	-	49.3	77.7	59.1	66.7	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K9-432AXSP16	45.2	72.2	54.7	61.8	-	45.5	72.3	54.8	62	-	73	17.2	2"	59	13.8	1-1/2"	88	24.1	2"
EAW-FD15S1ZK750K9-525AXSP16	53.5	84.1	64.2	72.3	141.2	54	84.3	64.4	72.5	141	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K9-532AXSP16	50.1	79.6	60.4	68.2	134.3	50.5	79.6	60.7	68.3	134.1	90	18.3	2"	72	12	2"	108	25.7	2"
EAW-FD15S1ZK750K9-625AXSP16	58.3	90.7	69.6	78.2	150.3	58.8	90.9	69.9	78.4	150.2	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW-FD15S1ZK750K9-632AXSP16	55.5	87.4	66.6	75.1	146	56	87.4	66.9	75.3	145.7	113	20	2"	90	13.2	2"	135	22.5	3"
EAW																			

EAW-FD15S2PB370K4-625AXSP12	90.1	137.4	106.1	118.7	225.1	90.4	137.1	106.3	118.5	224.1	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB370K4-632AXSP12	86.2	132.7	102.1	114.4	219.4	86.5	132.6	102.3	114.4	218.7	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB370K5-425AXSP12	77.2	120.4	92	103.4	-	77.4	120.4	92	103.5	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB370K5-432AXSP12	71.7	112.7	85.8	96.6	-	71.9	112.5	85.9	96.8	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB370K5-525AXSP12	84.8	130.9	100.5	112.7	-	85.2	130.9	100.8	112.8	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB370K5-532AXSP12	80.1	124.6	95.4	107.1	-	80.3	124.5	95.5	107.2	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB370K5-625AXSP12	90.1	137.4	106.1	118.7	225.1	90.4	137.1	106.3	118.5	224.1	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB370K5-632AXSP12	86.2	132.7	102.1	114.4	219.4	86.5	132.6	102.3	114.4	218.7	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB370K8-425AXSP12	77.2	120.4	92	103.4	-	77.4	120.4	92	103.5	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB370K8-432AXSP12	71.7	112.7	85.8	96.6	-	71.9	112.5	85.9	96.8	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB370K8-525AXSP12	84.8	130.9	100.5	112.7	-	85.2	130.9	100.8	112.8	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB370K8-532AXSP12	80.1	124.6	95.4	107.1	-	80.3	124.5	95.5	107.2	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB370K8-632AXSP12	90.1	137.4	106.1	118.7	225.1	90.4	137.1	106.3	118.5	224.1	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB370K8-632AXSP12	86.2	132.7	102.1	114.4	219.4	86.5	132.6	102.3	114.4	218.7	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400B3-425AXSP12	76	118.6	90.7	101.8	-	76.4	118.7	90.9	102.1	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400B3-432AXSP12	71.1	111.7	85.1	95.9	-	71.5	111.8	85.3	96	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400B3-525AXSP08	-	-	-	-	-	-	-	-	-	-	169	14.2	3"	135	9.3	3"	203	19.9	3"
EAW-FD15S2PB400B3-532AXSP12	78.7	122.3	93.5	105.2	-	79.1	122.3	93.9	105.4	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	15.1	3"	162	9.9	3"	244	21.2	3"
EAW-FD15S2PB400B3-632AXSP08	-	-	-	-	-	-	-	-	-	-	203	15.1	3"	162	9.9	3"	244	21.2	3"
EAW-FD15S2PB400C3-425AXSP08	75	119.9	90.9	102.7	203.3	75.9	120.2	91.5	103.1	203.4	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB400C3-432AXSP12	73.5	115.8	88	99.2	-	73.9	115.7	88.2	99.3	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400C3-525AXSP12	86	132.6	101.9	114.2	-	86.5	133	102.3	114.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400C3-532AXSP12	81.7	127	97.2	109.3	-	82.1	127.2	97.5	109.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400C3-625AXSP12	90.4	137.7	106.5	118.9	225.6	90.9	138	106.8	119.3	225.6	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400C3-632AXSP12	87.2	134.3	103.3	115.7	222.2	87.8	134.6	103.7	116.1	222	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400C9-425AXSP08	75	119.9	90.9	102.7	203.3	75.9	120.2	91.5	103.1	203.4	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB400C9-432AXSP12	73.5	115.8	88	99.2	-	73.9	115.7	88.2	99.3	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400C9-525AXSP12	86	132.6	101.9	114.2	-	86.5	133	102.3	114.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400C9-532AXSP12	81.7	127	97.2	109.3	-	82.1	127.2	97.5	109.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400C9-625AXSP12	90.4	137.7	106.5	118.9	225.6	90.9	138	106.8	119.3	225.6	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400C9-632AXSP12	87.2	134.3	103.3	115.7	222.2	87.8	134.6	103.7	116.1	222	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400K3-425AXSP12	77.2	120.4	92	103.4	-	77.4	120.4	92	103.5	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400K3-432AXSP12	71.7	112.7	85.8	96.6	-	71.9	112.5	85.9	96.8	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400K3-525AXSP12	84.8	130.9	100.5	112.7	-	85.2	130.9	100.8	112.8	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400K3-532AXSP12	80.1	124.6	95.4	107.1	-	80.3	124.5	95.5	107.2	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400K3-625AXSP12	90.1	137.4	106.1	118.7	225.1	90.4	137.1	106.3	118.5	224.1	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400K3-632AXSP12	86.2	132.7	102.1	114.4	219.4	86.5	132.6	102.3	114.4	218.7	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400K9-425AXSP12	77.2	120.4	92	103.4	-	77.4	120.4	92	103.5	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400K9-432AXSP12	71.7	112.7	85.8	96.6	-	71.9	112.5	85.9	96.8	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400K9-525AXSP12	84.8	130.9	100.5	112.7	-	85.2	130.9	100.8	112.8	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400K9-532AXSP12	80.1	124.6	95.4	107.1	-	80.3	124.5	95.5	107.2	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400K9-625AXSP12	90.1	137.4	106.1	118.7	225.1	90.4	137.1	106.3	118.5	224.1	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400K9-632AXSP12	86.2	132.7	102.1	114.4	219.4	86.5	132.6	102.3	114.4	218.7	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400R3-425AXSP12	77.9	121.7	93	104.6	-	78.2	121.8	93.2	104.6	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400R3-432AXSP12	72.4	113.9	86.7	97.7	-	72.7	113.8	86.8	97.9	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB400R3-525AXSP12	85.7	132.1	101.6	113.8	-	85.9	132.1	101.7	114	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400R3-532AXSP12	80.9	125.9	96.3	108.2	-	81.1	125.8	96.4	108.3	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB400R3-625AXSP12	90.9	138.5	107.1	119.6	-	91.2	138.5	107.2	119.7	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB400R3-632AXSP12	87.1	134	103.1	115.5	221.7	87.4	134	103.2	115.6	221	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550B3-425AXSP08	77.4	123.7	93.6	105.8	210.1	77.6	123.7	93.6	105.8	210.1	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550B3-432AXSP12	76	118.9	91	102.7	-	76.5	120.1	91.5	103	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB550B3-525AXSP08	-	-	-	-	-	-	-	-	-	-	169	14.2	3"	135	9.3	3"	203	19.9	3"
EAW-FD15S2PB550B3-532AXSP12	-	-	-	-	-	84.5	131.2	100.6	113	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	15.1	3"	162	9.9	3"	244	21.2	3"
EAW-FD15S2PB550B3-632AXSP08	-	-	-	-	-	-	-	-	-	-	203	15.1	3"	162	9.9	3"	244	21.2	3"
EAW-FD15S2PB550C2-425AXSP08	83	132.8	100.3	113.5	-	84	133.3	101.1	114.2	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550C2-432AXSP08	76.8	123.9	93.5	105.9	212.1	77.6	124.4	94.1	106.4	212.4	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550C2-525AXSP12	95.3	147.7	113.3	127	-	96	148.1	113.7	127.4	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550C2-532AXSP12	90	140.6	107.4	120.9	-	90.6	140.8	107.7	121.2	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550C2-632AXSP12	-	-	-	-	-	97.1	149.7	115	129	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550C3-425AXSP08	83	132.8	100.3	113.5	-	84	133.3	101.1	114.2	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550C3-432AXSP08	76.8	123.9	93.5	105.9	212.1	77.6	124.4	94.1	106.4	212.4	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550C3-525AXSP12	95.3	147.7	113.3	127	-	96	148.1	113.7	127.4	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550C3-532AXSP12	90	140.6	107.4	120.9	-	90.6	140.8	107.7	121.2	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550C3-625AXSP08	-	-	-	-	-	97.1	149.7	115	129	-	203	15.1	3"	162	9.9	3"	244	21.2	3"
EAW-FD15S2PB550C3-632AXSP12	-	-	-	-	-	97.1	149.7	115	129	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550C4-425AXSP08	83	132.8	100.3	113.5</															

EAW-FD15S2PB550K4-432AXSP12	77.7	122.5	93.1	105	-	78	122.5	93.3	105.2	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB550K4-525AXSP12	92.2	142.6	109.5	122.7	-	92.6	142.8	109.6	123	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K4-532AXSP12	87	135.4	103.7	116.6	-	87.3	135.5	103.7	116.6	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K4-625AXSP12	97.9	149.6	115.6	129.2	-	98.4	149.8	115.9	129.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K4-632AXSP12	93.6	144.4	110.9	124.4	-	94	144.5	111.2	124.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K5-425AXSP08	79.9	127.7	96.6	109.1	216.9	80.7	128	97.3	109.7	216.8	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550K5-432AXSP12	77.7	122.5	93.1	105	-	78	122.5	93.3	105.2	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB550K5-525AXSP12	92.2	142.6	109.5	122.7	-	92.6	142.8	109.6	123	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K5-532AXSP12	87	135.4	103.7	116.6	-	87.3	135.5	103.7	116.6	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K5-625AXSP12	97.9	149.6	115.6	129.2	-	98.4	149.8	115.9	129.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K5-632AXSP12	93.6	144.4	110.9	124.4	-	94	144.5	111.2	124.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K8-425AXSP08	79.9	127.7	96.6	109.1	216.9	80.7	128	97.3	109.7	216.8	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550K8-432AXSP12	77.7	122.5	93.1	105	-	78	122.5	93.3	105.2	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB550K8-525AXSP12	92.2	142.6	109.5	122.7	-	92.6	142.8	109.6	123	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K8-532AXSP12	87	135.4	103.7	116.6	-	87.3	135.5	103.7	116.6	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K8-625AXSP12	97.9	149.6	115.6	129.2	-	98.4	149.8	115.9	129.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K8-632AXSP12	93.6	144.4	110.9	124.4	-	94	144.5	111.2	124.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K9-425AXSP08	79.9	127.7	96.6	109.1	216.9	80.7	128	97.3	109.7	216.8	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550K9-432AXSP12	77.7	122.5	93.1	105	-	78	122.5	93.3	105.2	-	90	21.2	2"	72	14	2"	108	29.8	2"
EAW-FD15S2PB550K9-525AXSP12	92.2	142.6	109.5	122.7	-	92.6	142.8	109.6	123	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K9-532AXSP12	87	135.4	103.7	116.6	-	87.3	135.5	103.7	116.6	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550K9-625AXSP12	97.9	149.6	115.6	129.2	-	98.4	149.8	115.9	129.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550K9-632AXSP12	93.6	144.4	110.9	124.4	-	94	144.5	111.2	124.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550R3-425AXSP08	81.3	130.1	98.3	111.3	221	82.2	130.3	98.9	111.7	221	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550R3-432AXSP08	75.1	121.2	91.4	103.5	207.2	75.9	121.5	92	104	207.2	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB550R3-525AXSP12	93.7	145.1	111.3	124.9	-	94.3	145.3	111.7	125.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550R3-532AXSP12	88.3	138	105.3	118.5	-	88.8	138	105.7	118.7	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB550R3-625AXSP12	99.5	152.3	117.4	131.5	-	100	152.5	117.8	131.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB550R3-632AXSP12	95.1	147	112.9	126.6	-	95.6	146.9	113.2	126.7	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K2-425AXSP08	83.9	134.3	101.5	114.8	-	84.9	134.9	102.2	115.5	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K2-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K2-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K2-532AXSP12	91	142.2	108.6	122.2	-	91.6	142.4	108.9	122.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K2-625AXSP12	102.3	156.8	120.8	135.3	-	103	157	121.2	135.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K2-632AXSP12	97.9	151.3	116	130.2	-	98.4	151.4	116.5	130.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K3-425AXSP08	83.9	134.3	101.5	114.8	-	84.9	134.9	102.2	115.5	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K3-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K3-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K3-532AXSP12	91	142.2	108.6	122.2	-	91.6	142.4	108.9	122.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K3-625AXSP12	102.3	156.8	120.8	135.3	-	103	157	121.2	135.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K3-632AXSP12	97.9	151.3	116	130.2	-	98.4	151.4	116.5	130.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K4-425AXSP08	83.9	134.3	101.5	114.8	-	84.9	134.9	102.2	115.5	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K4-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K4-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K4-532AXSP12	91	142.2	108.6	122.2	-	91.6	142.4	108.9	122.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K4-625AXSP12	102.3	156.8	120.8	135.3	-	103	157	121.2	135.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K4-632AXSP12	97.9	151.3	116	130.2	-	98.4	151.4	116.5	130.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K5-425AXSP08	83.9	134.3	101.5	114.8	-	84.9	134.9	102.2	115.5	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K5-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K5-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K5-532AXSP12	91	142.2	108.6	122.2	-	91.6	142.4	108.9	122.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K5-625AXSP12	102.3	156.8	120.8	135.3	-	103	157	121.2	135.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K5-632AXSP12	97.9	151.3	116	130.2	-	98.4	151.4	116.5	130.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K8-425AXSP08	83.9	134.3	101.5	114.8	-	84.9	134.9	102.2	115.5	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K8-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K8-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K8-532AXSP12	91	142.2	108.6	122.2	-	91.6	142.4	108.9	122.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K8-625AXSP12	102.3	156.8	120.8	135.3	-	103	157	121.2	135.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K8-632AXSP12	97.9	151.3	116	130.2	-	98.4	151.4	116.5	130.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K9-425AXSP08	83.9	134.3	101.5	114.8	-	84.9	134.9	102.2	115.5	-	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K9-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K9-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K9-532AXSP12	91	142.2	108.6	122.2	-	91.6	142.4	108.9	122.5	-	113	22.9	2"	90	15.1	2"	135	26.8	3"
EAW-FD15S2PB750K9-625AXSP12	102.3	156.8	120.8	135.3	-	103	157	121.2	135.6	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K9-632AXSP12	97.9	151.3	116	130.2	-	98.4	151.4	116.5	130.5	-	135	19.5	3"	108	16.4	2"	162	27.4	3"
EAW-FD15S2PB750K8-432AXSP08	77.7	125.2	94.4	107	214.6	78.5	125.8	95.1	107.5	214.5	135	13.4	3"	108	12.4	2"	162	18.8	3"
EAW-FD15S2PB750K8-525AXSP12	96.4	149.6	114.6	128.7	-	97	149.8	115.2	129.1	-									

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S2ZB370K4-425AXSP12	83.2	129.8	99.2	111.5	-	83.5	129.6	99.4	111.5	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB370K4-432AXSP12	77.3	121.6	92.6	104.2	-	77.5	121.2	92.6	104.2	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB370K4-525AXSP12	90.6	139.8	107.3	120.3	-	90.8	139.5	107.5	120.2	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB370K4-532AXSP12	85.3	132.6	101.6	114	-	85.6	132.6	101.7	114	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB370K4-625AXSP12	97.7	148.8	115.1	128.4	243.3	97.9	148.4	115.2	128.3	242.3	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB370K4-632AXSP12	93.3	143.5	110.6	123.8	237.1	93.6	143.4	110.6	123.6	236.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB370K5-425AXSP12	83.2	129.8	99.2	111.5	-	83.5	129.6	99.4	111.5	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB370K5-432AXSP12	77.3	121.6	92.6	104.2	-	77.5	121.2	92.6	104.2	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB370K5-525AXSP12	90.6	139.8	107.3	120.3	-	90.8	139.5	107.5	120.2	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB370K5-532AXSP12	85.3	132.6	101.6	114	-	85.6	132.6	101.7	114	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB370K5-625AXSP12	97.7	148.8	115.1	128.4	243.3	97.9	148.4	115.2	128.3	242.3	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB370K5-632AXSP12	93.3	143.5	110.6	123.8	237.1	93.6	143.4	110.6	123.6	236.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB370K8-425AXSP12	83.2	129.8	99.2	111.5	-	83.5	129.6	99.4	111.5	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB370K8-432AXSP12	77.3	121.6	92.6	104.2	-	77.5	121.2	92.6	104.2	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB370K8-525AXSP12	90.6	139.8	107.3	120.3	-	90.8	139.5	107.5	120.2	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB370K8-532AXSP12	85.3	132.6	101.6	114	-	85.6	132.6	101.7	114	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB370K8-625AXSP12	97.7	148.8	115.1	128.4	243.3	97.9	148.4	115.2	128.3	242.3	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB370K8-632AXSP12	93.3	143.5	110.6	123.8	237.1	93.6	143.4	110.6	123.6	236.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400B3-425AXSP12	87.2	129	98.6	110.9	-	83.1	129.1	98.9	110.9	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400B3-432AXSP12	77.2	121.3	92.4	104.1	-	77.5	121.3	92.6	104.1	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400B3-525AXSP12	89.2	137.2	105.6	118.3	-	89.5	137.4	105.9	118.5	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400B3-532AXSP12	84.7	131.6	100.8	113.2	-	85	131.6	100.9	113.2	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	225	15.8	3"	180	10.4	3"	270	18.7	4"
EAW-FD15S2ZB400B3-632AXSP12	91.7	141	108.7	121.6	232.7	92.2	141.1	108.9	121.7	232.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400C3-425AXSP12	85.7	133.7	102.2	115	-	86	133.7	102.4	114.9	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400C3-432AXSP12	79.7	125.3	95.4	107.5	-	80	125.3	95.5	107.6	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400C3-525AXSP12	92.7	143.1	110	123.3	-	93.1	143	110.2	123.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400C3-532AXSP12	87.7	136.5	104.4	117.3	-	88.1	136.4	104.5	117.4	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400C3-625AXSP12	99.1	151	116.9	130.5	247.3	99.6	151	117.2	130.6	246.8	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400C3-632AXSP12	95.4	146.9	113.1	126.7	242.5	95.8	146.7	113.3	126.6	242.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400C9-425AXSP12	85.7	133.7	102.2	115	-	86	133.7	102.4	114.9	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400C9-432AXSP12	79.7	125.3	95.4	107.5	-	80	125.3	95.5	107.6	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400C9-525AXSP12	92.7	143.1	110	123.3	-	93.1	143	110.2	123.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400C9-532AXSP12	87.7	136.5	104.4	117.3	-	88.1	136.4	104.5	117.4	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400K9-625AXSP12	99.1	151	116.9	130.5	247.3	99.6	151	117.2	130.6	246.8	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400K9-632AXSP12	95.4	146.9	113.1	126.7	242.5	95.8	146.7	113.3	126.6	242.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400K3-425AXSP12	83.2	129.8	99.2	111.5	-	83.5	129.6	99.4	111.5	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400K3-432AXSP12	77.3	121.6	92.6	104.2	-	77.5	121.2	92.6	104.2	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400K3-525AXSP12	90.6	139.8	107.3	120.3	-	90.8	139.5	107.5	120.2	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400K3-532AXSP12	85.3	132.6	101.6	114	-	85.6	132.6	101.7	114	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400K3-625AXSP12	97.7	148.8	115.1	128.4	243.3	97.9	148.4	115.2	128.3	242.3	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400K3-632AXSP12	93.3	143.5	110.6	123.8	237.1	93.6	143.4	110.6	123.6	236.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400K9-425AXSP12	83.2	129.8	99.2	111.5	-	83.5	129.6	99.4	111.5	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400K9-432AXSP12	77.3	121.6	92.6	104.2	-	77.5	121.2	92.6	104.2	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400K9-525AXSP12	90.6	139.8	107.3	120.3	-	90.8	139.5	107.5	120.2	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400K9-532AXSP12	85.3	132.6	101.6	114	-	85.6	132.6	101.7	114	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400K9-625AXSP12	97.7	148.8	115.1	128.4	243.3	97.9	148.4	115.2	128.3	242.3	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400K9-632AXSP12	93.3	143.5	110.6	123.8	237.1	93.6	143.4	110.6	123.6	236.2	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400R3-425AXSP12	84.2	131.4	100.4	112.9	-	84.6	131.3	100.5	112.9	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400R3-432AXSP12	78.3	123	93.6	105.5	-	78.6	122.9	93.8	105.6	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB400R3-525AXSP12	91.6	141.3	108.7	121.8	-	91.8	141.1	108.7	121.8	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400R3-532AXSP12	86.3	134.2	102.7	115.4	-	86.6	134	102.7	115.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB400R3-625AXSP12	98.8	150.3	116.3	129.8	246	99	150	116.3	129.8	245.1	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB400R3-632AXSP12	94.4	145.3	111.8	125.1	239.8	94.6	145	111.9	125	238.9	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550B3-425AXSP08	84.6	135.4	102.6	115.9	229.6	85.7	135.8	103.3	116.4	229.7	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550B3-432AXSP12	83	130.7	99.3	112	-	83.4	130.7	99.6	112.2	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550B3-525AXSP12	95.8	147.9	113.6	127.4	-	96.3	148.1	114	127.7	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550B3-532AXSP12	90.9	141.5	108.3	121.7	-	91.4	141.7	108.5	122	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	225	15.8	3"	180	10.4	3"	270	18.7	4"
EAW-FD15S2ZB550B3-632AXSP12	-	-	-	-	-	99.1	152	117	131.1	250.7	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550C2-425AXSP08	90.4	144.5	109.3	123.7	245.4	91.3	145	110	124.1	245.7	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550C2-432AXSP08	83.4	134.5	101.6	115	230	84.3	134.9	102.1	115.5	229.8	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550C2-525AXSP12	102.9	159.5	122.3	137.3	-	103.4	159.6	122.7	137.5	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550C2-532AXSP12	96.8	151.2	115.5	130	-	97.3	151.3	115.8	130	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550C2-625AXSP12	110.7	169.1	130.7	146	-	111.2	169.5	130.9	146.3	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550C2-632AXSP12	105.9	163.4	125.5	140.7															

EAW-FD15S2ZB550K2-632AXSP12	101.9	157.1	120.9	135.5	-	102.2	157	120.9	135.5	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K3-425AXSP08	86.5	138.3	104.7	118.3	234.7	87.3	138.6	105.4	118.8	234.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550K3-432AXSP12	84.2	132.6	100.8	113.8	-	84.5	132.7	101	113.8	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550K3-525AXSP12	99	153.1	117.4	131.7	-	99.4	153	117.7	131.8	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K3-532AXSP12	92.9	144.9	110.8	124.5	-	93.4	144.9	110.9	124.7	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K3-625AXSP12	106.7	163.1	125.9	140.7	-	107.1	162.8	126.1	140.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K3-632AXSP12	101.9	157.1	120.9	135.5	-	102.2	157	120.9	135.5	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K4-425AXSP08	86.5	138.3	104.7	118.3	234.7	87.3	138.6	105.4	118.8	234.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550K4-432AXSP12	84.2	132.6	100.8	113.8	-	84.5	132.7	101	113.8	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550K4-525AXSP12	99	153.1	117.4	131.7	-	99.4	153	117.7	131.8	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K4-532AXSP12	92.9	144.9	110.8	124.5	-	93.4	144.9	110.9	124.7	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K4-625AXSP12	106.7	163.1	125.9	140.7	-	107.1	162.8	126.1	140.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K4-632AXSP12	101.9	157.1	120.9	135.5	-	102.2	157	120.9	135.5	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K5-425AXSP08	86.5	138.3	104.7	118.3	234.7	87.3	138.6	105.4	118.8	234.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550K5-432AXSP12	84.2	132.6	100.8	113.8	-	84.5	132.7	101	113.8	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550K5-525AXSP12	99	153.1	117.4	131.7	-	99.4	153	117.7	131.8	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K5-532AXSP12	92.9	144.9	110.8	124.5	-	93.4	144.9	110.9	124.7	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K5-625AXSP12	106.7	163.1	125.9	140.7	-	107.1	162.8	126.1	140.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K5-632AXSP12	101.9	157.1	120.9	135.5	-	102.2	157	120.9	135.5	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K8-425AXSP08	86.5	138.3	104.7	118.3	234.7	87.3	138.6	105.4	118.8	234.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550K8-432AXSP12	84.2	132.6	100.8	113.8	-	84.5	132.7	101	113.8	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550K8-525AXSP12	99	153.1	117.4	131.7	-	99.4	153	117.7	131.8	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K8-532AXSP12	92.9	144.9	110.8	124.5	-	93.4	144.9	110.9	124.7	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K8-625AXSP12	106.7	163.1	125.9	140.7	-	107.1	162.8	126.1	140.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K8-632AXSP12	101.9	157.1	120.9	135.5	-	102.2	157	120.9	135.5	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K9-425AXSP08	86.5	138.3	104.7	118.3	234.7	87.3	138.6	105.4	118.8	234.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550K9-432AXSP12	84.2	132.6	100.8	113.8	-	84.5	132.7	101	113.8	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550K9-525AXSP12	99	153.1	117.4	131.7	-	99.4	153	117.7	131.8	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K9-532AXSP12	92.9	144.9	110.8	124.5	-	93.4	144.9	110.9	124.7	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550K9-625AXSP12	106.7	163.1	125.9	140.7	-	107.1	162.8	126.1	140.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550K9-632AXSP12	101.9	157.1	120.9	135.5	-	102.2	157	120.9	135.5	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550R3-425AXSP08	88.1	141	106.7	120.6	239.7	89.1	141.4	107.2	121.1	239.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB550R3-432AXSP12	85.8	135.2	102.8	115.9	-	86.1	135.1	103	116	-	101	22.1	2"	81	14.6	2"	122	26.5	3"
EAW-FD15S2ZB550R3-525AXSP12	100.8	156.1	119.8	134.2	-	101.1	156.1	120	134.4	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550R3-532AXSP12	94.6	147.7	112.8	126.9	-	95.1	147.8	113	127.1	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB550R3-625AXSP12	108.6	166.1	128.2	143.2	-	109.1	166.1	128.4	143.4	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB550R3-632AXSP12	103.9	160.1	123.1	137.9	-	104.1	160	123.2	138.1	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K2-425AXSP08	91.4	146.2	110.5	125.1	248.5	92.4	146.5	111.2	125.6	248.5	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K2-432AXSP08	84.4	136.3	102.7	116.5	233.2	85.4	136.7	103.4	117	233.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K2-525AXSP12	104.1	161.5	123.8	138.8	-	104.7	161.6	124	139.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K2-532AXSP12	97.9	152.9	116.8	131.4	-	98.4	153.1	117.1	131.6	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K2-625AXSP12	112	171.5	132.3	148.1	-	112.7	171.6	132.6	148.2	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K2-632AXSP12	107.1	165.4	127	142.4	-	107.6	165.6	127.4	142.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K3-425AXSP08	91.4	146.2	110.5	125.1	248.5	92.4	146.5	111.2	125.6	248.5	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K3-432AXSP08	84.4	136.3	102.7	116.5	233.2	85.4	136.7	103.4	117	233.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K3-525AXSP12	104.1	161.5	123.8	138.8	-	104.7	161.6	124	139.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K3-625AXSP12	97.9	152.9	116.8	131.4	-	98.4	153.1	117.1	131.6	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K3-632AXSP12	112	171.5	132.3	148.1	-	112.7	171.6	132.6	148.2	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K3-632AXSP12	107.1	165.4	127	142.4	-	107.6	165.6	127.4	142.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K4-425AXSP08	91.4	146.2	110.5	125.1	248.5	92.4	146.5	111.2	125.6	248.5	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K4-432AXSP08	84.4	136.3	102.7	116.5	233.2	85.4	136.7	103.4	117	233.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K4-525AXSP12	104.1	161.5	123.8	138.8	-	104.7	161.6	124	139.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K4-532AXSP12	97.9	152.9	116.8	131.4	-	98.4	153.1	117.1	131.6	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K4-625AXSP12	112	171.5	132.3	148.1	-	112.7	171.6	132.6	148.2	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K4-632AXSP12	107.1	165.4	127	142.4	-	107.6	165.6	127.4	142.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K5-425AXSP08	91.4	146.2	110.5	125.1	248.5	92.4	146.5	111.2	125.6	248.5	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K5-432AXSP08	84.4	136.3	102.7	116.5	233.2	85.4	136.7	103.4	117	233.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K5-525AXSP12	104.1	161.5	123.8	138.8	-	104.7	161.6	124	139.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K5-532AXSP12	97.9	152.9	116.8	131.4	-	98.4	153.1	117.1	131.6	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K5-625AXSP12	112	171.5	132.3	148.1	-	112.7	171.6	132.6	148.2	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K5-632AXSP12	107.1	165.4	127	142.4	-	107.6	165.6	127.4	142.8	-	152	19.9	3"	122	13.1	3"	183	27.9	3"
EAW-FD15S2ZB750K8-425AXSP08	91.4	146.2	110.5	125.1	248.5	92.4	146.5	111.2	125.6	248.5	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K8-432AXSP08	84.4	136.3	102.7	116.5	233.2	85.4	136.7	103.4	117	233.3	152	13.8	3"	122	9.1	3"	183	19.4	3"
EAW-FD15S2ZB750K8-525AXSP12	104.1	161.5	123.8	138.8	-	104.7	161.6	124	139.3	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K8-532AXSP12	97.9	152.9	116.8	131.4	-	98.4	153.1	117.1	131.6	-	124	19.3	3"	99	15.8	2"	149	27.1	3"
EAW-FD15S2ZB750K8-625AXSP12	112	171.5	132.3	148.1	-	112.7													

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S2ZK370C8-625AXSP12	108	163.7	126.8	141.5	-	108.4	163.6	126.9	141.6	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370C8-632AXSP12	103.8	158.8	122.4	137	-	103.8	158.4	122.3	136.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K2-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K2-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K2-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K2-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K2-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K2-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K4-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K4-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K4-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K4-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K4-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K4-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K5-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K5-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K5-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K5-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K5-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K5-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-625AXSP12	105.5	159.7	123.9	138.2	-	105.5	159.2	123.6	137.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-632AXSP12	100.8	154.1	118.9	133	253.8	100.9	153.7	118.8	132.7	252.2	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK370K8-425AXSP08	85.8	135.9	103.3	116.4	228.8	86.3	135.7	103.5	116.6	227.9	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK370K8-432AXSP12	83.2	130.1	99.4	111.6	-	83.2	129.7	99.1	111.5	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK370K8-525AXSP12	97.7	149.9	115.5	129.3	-	97.8	149.4	115.3	129.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK370K8-532AXSP12	92	142.4	109.3	122.6	-	92.2	141.9	109.1	122.3	-	124								

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S2ZK550C9-532AXSP12	105.1	163.5	125	140.5	-	105.3	163.1	125.1	140.4	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550C9-625AXSP12	120.6	183.8	142.1	158.8	-	121.1	183.8	142.4	158.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550C9-632AXSP12	115.4	177.4	136.5	152.7	-	115.6	176.9	136.5	152.7	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K2-425AXSP08	94.2	149.1	113.2	127.8	252.2	94.9	149.2	113.7	128.1	251.3	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K2-432AXSP08	87	138.9	105.2	119	236.4	87.6	139.1	105.6	119.2	235.5	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K2-525AXSP12	107.1	165	126.7	142.1	-	107.2	164.5	126.7	142.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K2-532AXSP12	100.6	156.2	119.6	134.4	-	100.8	156	119.6	134.2	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K2-625AXSP12	115.7	176	136.3	152	-	115.9	175.6	136.2	151.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K2-632AXSP12	110.3	169.3	130.5	146.1	-	110.6	168.9	130.4	145.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K3-425AXSP08	94.2	149.1	113.2	127.8	252.2	94.9	149.2	113.7	128.1	251.3	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K3-432AXSP08	87	138.9	105.2	119	236.4	87.6	139.1	105.6	119.2	235.5	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K3-525AXSP12	107.1	165	126.7	142.1	-	107.2	164.5	126.7	142.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K3-532AXSP12	100.6	156.2	119.6	134.4	-	100.8	156	119.6	134.2	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K3-625AXSP12	115.7	176	136.3	152	-	115.9	175.6	136.2	151.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K3-632AXSP12	110.3	169.3	130.5	146.1	-	110.6	168.9	130.4	145.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K4-425AXSP08	94.2	149.1	113.2	127.8	252.2	94.9	149.2	113.7	128.1	251.3	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K4-432AXSP08	87	138.9	105.2	119	236.4	87.6	139.1	105.6	119.2	235.5	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K4-525AXSP12	107.1	165	126.7	142.1	-	107.2	164.5	126.7	142.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K4-532AXSP12	100.6	156.2	119.6	134.4	-	100.8	156	119.6	134.2	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K4-625AXSP12	115.7	176	136.3	152	-	115.9	175.6	136.2	151.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K4-632AXSP12	110.3	169.3	130.5	146.1	-	110.6	168.9	130.4	145.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K5-425AXSP08	94.2	149.1	113.2	127.8	252.2	94.9	149.2	113.7	128.1	251.3	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K5-432AXSP08	87	138.9	105.2	119	236.4	87.6	139.1	105.6	119.2	235.5	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K5-525AXSP12	107.1	165	126.7	142.1	-	107.2	164.5	126.7	142.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K5-532AXSP12	100.6	156.2	119.6	134.4	-	100.8	156	119.6	134.2	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K5-625AXSP12	115.7	176	136.3	152	-	115.9	175.6	136.2	151.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K5-632AXSP12	110.3	169.3	130.5	146.1	-	110.6	168.9	130.4	145.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K8-425AXSP08	94.2	149.1	113.2	127.8	252.2	94.9	149.2	113.7	128.1	251.3	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K8-432AXSP08	87	138.9	105.2	119	236.4	87.6	139.1	105.6	119.2	235.5	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K8-525AXSP12	107.1	165	126.7	142.1	-	107.2	164.5	126.7	142.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K8-532AXSP12	100.6	156.2	119.6	134.4	-	100.8	156	119.6	134.2	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K8-625AXSP12	115.7	176	136.3	152	-	115.9	175.6	136.2	151.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K8-632AXSP12	110.3	169.3	130.5	146.1	-	110.6	168.9	130.4	145.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K9-425AXSP08	94.2	149.1	113.2	127.8	252.2	94.9	149.2	113.7	128.1	251.3	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K9-432AXSP08	87	138.9	105.2	119	236.4	87.6	139.1	105.6	119.2	235.5	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550K9-525AXSP12	107.1	165	126.7	142.1	-	107.2	164.5	126.7	142.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K9-532AXSP12	100.6	156.2	119.6	134.4	-	100.8	156	119.6	134.2	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550K9-625AXSP12	115.7	176	136.3	152	-	115.9	175.6	136.2	151.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550K9-632AXSP12	110.3	169.3	130.5	146.1	-	110.6	168.9	130.4	145.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550R3-425AXSP08	96.1	152.4	115.6	130.5	-	96.9	152.3	116	130.7	-	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550R3-432AXSP08	88.8	142	107.4	121.4	241.4	89.4	141.9	107.7	121.7	240.7	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK550R3-525AXSP08	104.5	164.3	125.5	141.2	275	105.3	164.4	125.8	141.5	274.3	186	15.8	3"	149	10.4	3"	223	22.2	3"
EAW-FD15S2ZK550R3-532AXSP12	102.6	159.5	122.1	137.2	-	102.9	159.1	122.1	137	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK550R3-625AXSP12	118	179.6	139	155.3	-	118.3	179.3	139	155	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK550R3-632AXSP12	112.5	172.8	133.1	149.1	-	112.8	172.5	133	148.8	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK750C4-425AXSP12	107.1	167.4	127.9	143.8	-	107.6	167.3	128	144	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK750C4-432AXSP12	99.1	156.1	118.7	133.7	-	99.5	156	118.9	133.9	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK750C4-525AXSP12	116.2	179.6	137.9	154.8	-	116.8	179.9	138.4	155.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK750C4-532AXSP12	109.4	170.4	130.2	146.5	-	109.9	170.3	130.6	146.6	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK750C4-632AXSP12	119.6	184.1	141.7	158.6	-	120	184.1	141.8	159	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK750C5-425AXSP12	107.1	167.4	127.9	143.8	-	107.6	167.3	128	144	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK750C5-432AXSP12	99.1	156.1	118.7	133.7	-	99.5	156	118.9	133.9	-	101	23.8	2"	81	15.7	2"	122	28.9	3"
EAW-FD15S2ZK750C5-525AXSP12	116.2	179.6	137.9	154.8	-	116.8	179.9	138.4	155.1	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK750C5-532AXSP12	109.4	170.4	130.2	146.5	-	109.9	170.3	130.6	146.6	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK750C5-632AXSP12	119.6	184.1	141.7	158.6	-	120	184.1	141.8	159	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK750K2-425AXSP08	99.9	158.3	120.1	135.7	-	100.7	158.5	120.6	136	-	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK750K2-432AXSP08	92.4	147.7	111.7	126.3	251.6	93.1	147.7	112	126.6	251.1	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK750K2-525AXSP08	108.5	170.6	130.2	146.5	286.1	109.5	170.9	130.6	147	285.6	186	15.8	3"	149	10.4	3"	223	22.2	3"
EAW-FD15S2ZK750K2-532AXSP12	106.4	165.5	126.6	142.4	-	106.8	165.2	126.9	142.4	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK750K2-625AXSP12	122.2	186.2	144	160.8	-	122.7	186.1	144.2	160.9	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK750K2-632AXSP12	116.6	179.3	138.1	154.6	-	117	179.2	138.2	154.6	-	152	21.6	3"	122	14.3	3"	183	30.3	3"
EAW-FD15S2ZK750K3-425AXSP08	99.9	158.3	120.1	135.7	-	100.7	158.5	120.6	136	-	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK750K3-432AXSP08	92.4	147.7	111.7	126.3	251.6	93.1	147.7	112	126.6	251.1	152	14.9	3"	122	9.9	3"	183	21	3"
EAW-FD15S2ZK750K3-525AXSP08	108.5	170.6	130.2	146.5	286.1	109.5	170.9	130.6	147	285.6	186	15.8	3"	149	10.4	3"	223	22.2	3"
EAW-FD15S2ZK750K3-532AXSP12	106.4	165.5	126.6	142.4	-	106.8	165.2	126.9	142.4	-	124	21	3"	99	17	2"	149	29.5	3"
EAW-FD15S2ZK750K3-625AXSP12</																			

EAW-FD15S3PB370C2-625AXSP08	135.2	206	159.3	177.8	337.6	136	206.4	160	178.4	337.9	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C2-632AXSP08	130.4	200.9	154.7	173.3	332.4	131.3	201.3	155	173.6	332.2	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C4-425AXSP08	114.2	180.8	137.1	154.8	-	115.1	181.3	138.1	155.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD15S3PB370C4-432AXSP08	109.9	173	131.5	148.3	-	110.4	173	131.9	148.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370C4-525AXSP08	128.6	198.6	152.4	170.8	-	129.3	198.8	153	171.5	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370C4-532AXSP08	122.1	189.9	145.5	163.4	-	122.8	190.3	145.7	163.7	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370C4-625AXSP08	135.2	206	159.3	177.8	337.6	136	206.4	160	178.4	337.9	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C4-632AXSP08	130.4	200.9	154.7	173.3	332.4	131.3	201.3	155	173.6	332.2	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C5-425AXSP06	114.2	180.8	137.1	154.8	-	115.1	181.3	138.1	155.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD15S3PB370C5-432AXSP08	109.9	173	131.5	148.3	-	110.4	173	131.9	148.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370C5-525AXSP08	128.6	198.6	152.4	170.8	-	129.3	198.8	153	171.5	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370C5-532AXSP08	122.1	189.9	145.5	163.4	-	122.8	190.3	145.7	163.7	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370C5-625AXSP08	135.2	206	159.3	177.8	337.6	136	206.4	160	178.4	337.9	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C5-632AXSP08	130.4	200.9	154.7	173.3	332.4	131.3	201.3	155	173.6	332.2	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C8-425AXSP06	114.2	180.8	137.1	154.8	-	115.1	181.3	138.1	155.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD15S3PB370C8-432AXSP08	109.9	173	131.5	148.3	-	110.4	173	131.9	148.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370C8-525AXSP08	128.6	198.6	152.4	170.8	-	129.3	198.8	153	171.5	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370C8-532AXSP08	122.1	189.9	145.5	163.4	-	122.8	190.3	145.7	163.7	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370C8-625AXSP08	135.2	206	159.3	177.8	337.6	136	206.4	160	178.4	337.9	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370C8-632AXSP08	130.4	200.9	154.7	173.3	332.4	131.3	201.3	155	173.6	332.2	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K2-425AXSP08	115.3	180	137.5	154.8	-	115.7	180	137.8	154.7	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K2-432AXSP08	107	168.4	128.2	144.5	-	107.5	168.4	128.4	144.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K2-525AXSP08	126.8	195.8	150.6	168.7	-	127.4	195.7	150.7	168.6	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K2-532AXSP08	119.8	186.3	142.6	160.1	-	120.3	186.2	142.7	160.2	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K2-625AXSP08	134.7	205.5	158.9	177.5	336.8	135.4	205.4	159	177.6	335.8	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K2-632AXSP08	128.9	198.8	152.9	171.3	328.3	129.4	198.3	153	171.3	327.6	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K4-425AXSP08	115.3	180	137.5	154.8	-	115.7	180	137.8	154.7	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K4-432AXSP08	107	168.4	128.2	144.5	-	107.5	168.4	128.4	144.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K4-525AXSP08	126.8	195.8	150.6	168.7	-	127.4	195.7	150.7	168.6	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K4-532AXSP08	119.8	186.3	142.6	160.1	-	120.3	186.2	142.7	160.2	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K4-625AXSP08	134.7	205.5	158.9	177.5	336.8	135.4	205.4	159	177.6	335.8	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K4-632AXSP08	128.9	198.8	152.9	171.3	328.3	129.4	198.3	153	171.3	327.6	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K5-425AXSP08	115.3	180	137.5	154.8	-	115.7	180	137.8	154.7	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K5-432AXSP08	107	168.4	128.2	144.5	-	107.5	168.4	128.4	144.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K5-525AXSP08	126.8	195.8	150.6	168.7	-	127.4	195.7	150.7	168.6	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K5-532AXSP08	119.8	186.3	142.6	160.1	-	120.3	186.2	142.7	160.2	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K5-625AXSP08	134.7	205.5	158.9	177.5	336.8	135.4	205.4	159	177.6	335.8	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K5-632AXSP08	128.9	198.8	152.9	171.3	328.3	129.4	198.3	153	171.3	327.6	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K8-425AXSP08	115.3	180	137.5	154.8	-	115.7	180	137.8	154.7	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K8-432AXSP08	107	168.4	128.2	144.5	-	107.5	168.4	128.4	144.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB370K8-525AXSP08	126.8	195.8	150.6	168.7	-	127.4	195.7	150.7	168.6	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K8-532AXSP08	119.8	186.3	142.6	160.1	-	120.3	186.2	142.7	160.2	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB370K8-625AXSP08	134.7	205.5	158.9	177.5	336.8	135.4	205.4	159	177.6	335.8	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB370K8-632AXSP08	128.9	198.8	152.9	171.3	328.3	129.4	198.3	153	171.3	327.6	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB400B3-425AXSP08	113.6	177.2	135.5	152.4	-	114.1	177.8	135.9	152.8	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB400B3-432AXSP08	106.2	167	127.2	143.4	-	106.8	167.1	127.6	143.8	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB400B3-525AXSP06	-	-	-	-	-	-	-	-	-	-	225	16.6	3"	180	10.9	3"	270	19.8	4"
EAW-FD15S3PB400B3-532AXSP08	117.6	182.8	140	157.2	-	118.3	182.9	140.3	157.5	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	270	14.6	4"	216	11.9	3"	325	20.6	4"
EAW-FD15S3PB400B3-632AXSP06	-	-	-	-	-	-	-	-	-	-	270	14.6	4"	216	11.9	3"	325	20.6	4"
EAW-FD15S3PB400C3-425AXSP06	114.2	180.8	137.1	154.8	-	115.1	181.3	138.1	155.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD15S3PB400C3-432AXSP08	109.9	173	131.5	148.3	-	110.4	173	131.9	148.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB400C3-525AXSP08	128.6	198.6	152.4	170.8	-	129.3	198.8	153	171.5	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB400C3-532AXSP08	122.1	189.9	145.5	163.4	-	122.8	190.3	145.7	163.7	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB400C3-625AXSP08	135.2	206	159.3	177.8	337.6	136	206.4	160	178.4	337.9	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB400C3-632AXSP08	130.4	200.9	154.7	173.3	332.4	131.3	201.3	155	173.6	332.2	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB400C9-425AXSP06	114.2	180.8	137.1	154.8	-	115.1	181.3	138.1	155.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD15S3PB400C9-432AXSP08	109.9	173	131.5	148.3	-	110.4	173	131.9	148.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB400C9-525AXSP08	128.6	198.6	152.4	170.8	-	129.3	198.8	153	171.5	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB400C9-532AXSP08	122.1	189.9	145.5	163.4	-	122.8	190.3	145.7	163.7	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB400C9-625AXSP08	135.2	206	159.3	177.8	337.6	136	206.4	160	178.4	337.9	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB400C9-632AXSP08	130.4	200.9	154.7	173.3	332.4	131.3	201.3	155	173.6	332.2	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD15S3PB400K3-425AXSP08	115.3	180	137.5	154.8	-	115.7	180	137.8	154.7	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB400K3-432AXSP08	107	168.4	128.2	144.5	-	107.5	168.4	128.4	144.6	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD15S3PB400K3-525AXSP08	126.8	195.8	150.6	168.7	-	127.4	195.7	150.7	168.6	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD15S3PB400K3-532AXSP08	119.8	186.3	142.6	160.1	-	120.3	186.2	142.7	160.2	-	169	19.3	3"	135	12.7	3"	203	27.1</	

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553PB550C4-632AXSP08	-	-	-	-	-	145.2	223.8	172	192.9	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550C5-425AXSP06	126.1	199.9	151.6	171.3	-	127.3	200.8	152.7	172.3	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550C8-432AXSP06	117	186.8	141.2	159.7	-	118	187.4	141.9	160.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550C5-525AXSP08	142.5	220.9	169.4	190.2	-	143.5	221.4	170	190.8	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550C5-532AXSP08	134.5	210.1	160.5	180.6	-	135.4	210.8	161.3	181.1	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550C5-632AXSP08	-	-	-	-	-	145.2	223.8	172	192.9	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550C8-432AXSP06	126.1	199.9	151.6	171.3	-	127.3	200.8	152.7	172.3	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550C8-432AXSP06	117	186.8	141.2	159.7	-	118	187.4	141.9	160.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550C8-525AXSP08	142.5	220.9	169.4	190.2	-	143.5	221.4	170	190.8	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550C8-532AXSP08	134.5	210.1	160.5	180.6	-	135.4	210.8	161.3	181.1	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550C8-632AXSP08	-	-	-	-	-	145.2	223.8	172	192.9	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550C9-425AXSP06	126.1	199.9	151.6	171.3	-	127.3	200.8	152.7	172.3	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550C9-432AXSP06	117	186.8	141.2	159.7	-	118	187.4	141.9	160.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550C9-525AXSP08	142.5	220.9	169.4	190.2	-	143.5	221.4	170	190.8	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550C9-532AXSP08	134.5	210.1	160.5	180.6	-	135.4	210.8	161.3	181.1	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550C9-625AXSP06	-	-	-	-	-	-	-	-	-	-	270	14.6	4"	216	11.9	3"	325	20.6	4"
EAW-FD1553PB550C9-632AXSP08	-	-	-	-	-	145.2	223.8	172	192.9	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K2-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K2-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K2-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K2-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K2-625AXSP08	146.5	224.1	172.9	193.2	-	147.2	224	173.3	193.6	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K2-632AXSP08	139.9	215.9	165.9	186	-	140.7	216.1	166.3	186.4	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K3-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K3-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K3-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K3-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K3-625AXSP08	146.5	224.1	172.9	193.2	-	147.2	224	173.3	193.6	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K3-632AXSP08	139.9	215.9	165.9	186	-	140.7	216.1	166.3	186.4	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K4-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K4-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K4-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K4-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K4-625AXSP08	146.5	224.1	172.9	193.2	-	147.2	224	173.3	193.6	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K4-632AXSP08	139.9	215.9	165.9	186	-	140.7	216.1	166.3	186.4	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K5-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K5-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K5-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K5-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K5-632AXSP08	146.5	224.1	172.9	193.2	-	147.2	224	173.3	193.6	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K6-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K6-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K6-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K6-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K8-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K8-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K8-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K8-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K9-425AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550K9-432AXSP08	116.1	183.1	139.2	157	-	116.6	183.1	139.5	157.1	-	135	18.6	3"	108	15.8	2"	162	26	3"
EAW-FD1553PB550K9-525AXSP08	137.8	213.3	163.7	183.7	-	138.6	213.6	164.2	183.9	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K9-532AXSP08	129.9	202.8	154.9	174.2	-	130.5	202.7	155.3	174.3	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550K9-625AXSP08	146.5	224.1	172.9	193.2	-	147.2	224	173.3	193.6	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K9-632AXSP08	139.9	215.9	165.9	186	-	140.7	216.1	166.3	186.4	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550K9-632AXSP06	121.4	192.3	146	164.6	-	122.4	193	146.8	165.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550R3-425AXSP06	123.5	195.8	148.5	167.9	-	124.5	196.6	149.4	168.5	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550R3-432AXSP06	114.3	182.7	138.1	156.3	-	115.4	183.1	138.8	156.9	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB550R3-525AXSP08	140.3	217.3	166.4	186.8	-	140.9	217.3	167	187.4	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550R3-532AXSP08	132	206.3	157.4	177.1	-	132.7	206.3	158	177.4	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB550R3-625AXSP08	149	227.9	175.9	196.6	-	149.6	228.2	176.4	197.1	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB550R3-632AXSP08	142.3	219.8	168.8	189.3	-	142.9	219.8	169.2	189.4	-	203	20.2	3"	162	13.3	3"	244	28.4	3"
EAW-FD1553PB750K2-425AXSP06	127.5	202.2	153.4	173.2	-	128.7	203.2	154.4	174.3	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB750K2-432AXSP06	118.1	188.9	142.6	161.4	-	119.3	189.4	143.5	162.1	-	180	15.3	3"	144	10.1	3"	216	21.5	3"
EAW-FD1553PB750K2-525AXSP08	144.4	223.7	171.6	192.4	-	145.3	224.4	172.1	193	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB750K2-532AXSP08	135.9	212.5	162.2	182.6	-	136.9	212.9	163.1	183.2	-	169	19.3	3"	135	12.7	3"	203	27.1	3"
EAW-FD1553PB750K2-625AXSP08	153	234.5	180.9	202.3	-	154	234.8	181.3	202.8	-	203	20.2	3"	162	13.3	3"	244	28.4	3"

EAW-FD15S3ZB370C2-425AXSP08	128	200.2	152.7	171.8	-	128.5	199.8	153	172.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C2-432AXSP08	119.1	187.3	142.7	160.8	-	119.6	187.2	142.8	160.7	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C2-525AXSP08	138.5	214	164.4	184.4	-	139.2	214.1	164.8	184.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C2-532AXSP08	131.3	204	156	175.6	-	131.6	204	156.2	175.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C2-625AXSP08	147.4	224.8	173.6	194.1	368.3	148.2	224.8	174.1	194.3	367.5	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C2-632AXSP08	141.8	218.2	167.9	188	360.9	142.4	218.2	168.1	188.3	360	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C4-425AXSP08	128	200.2	152.7	171.8	-	128.5	199.8	153	172.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C4-432AXSP08	119.1	187.3	142.7	160.8	-	119.6	187.2	142.8	160.7	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C4-525AXSP08	138.5	214	164.4	184.4	-	139.2	214.1	164.8	184.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C4-532AXSP08	131.3	204	156	175.6	-	131.6	204	156.2	175.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C4-625AXSP08	147.4	224.8	173.6	194.1	368.3	148.2	224.8	174.1	194.3	367.5	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C4-632AXSP08	141.8	218.2	167.9	188	360.9	142.4	218.2	168.1	188.3	360	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C5-425AXSP08	128	200.2	152.7	171.8	-	128.5	199.8	153	172.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C5-432AXSP08	119.1	187.3	142.7	160.8	-	119.6	187.2	142.8	160.7	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C5-425AXSP08	138.5	214	164.4	184.4	-	139.2	214.1	164.8	184.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C5-532AXSP08	131.3	204	156	175.6	-	131.6	204	156.2	175.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C5-625AXSP08	147.4	224.8	173.6	194.1	368.3	148.2	224.8	174.1	194.3	367.5	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C5-632AXSP08	141.8	218.2	167.9	188	360.9	142.4	218.2	168.1	188.3	360	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C8-425AXSP08	128	200.2	152.7	171.8	-	128.5	199.8	153	172.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C8-432AXSP08	119.1	187.3	142.7	160.8	-	119.6	187.2	142.8	160.7	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370C8-525AXSP08	138.5	214	164.4	184.4	-	139.2	214.1	164.8	184.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C8-532AXSP08	131.3	204	156	175.6	-	131.6	204	156.2	175.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370C8-625AXSP08	147.4	224.8	173.6	194.1	368.3	148.2	224.8	174.1	194.3	367.5	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370C8-632AXSP08	141.8	218.2	167.9	188	360.9	142.4	218.2	168.1	188.3	360	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K2-425AXSP08	124.6	194.4	148.5	167	-	124.8	194.1	148.6	167	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K2-432AXSP08	115.7	181.7	138.3	155.9	-	115.9	181.4	138.3	155.6	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K2-525AXSP08	135.5	209	160.8	180.2	-	135.8	208.6	160.7	180	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K2-532AXSP08	127.8	198.6	152.1	170.8	-	127.9	198.2	152.1	170.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K2-625AXSP08	145.3	221.2	171.1	191.1	362.4	145.6	220.8	171.1	191	360.9	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K2-632AXSP08	138.6	213.5	164.4	184	352.9	139.1	213	164.2	183.8	351.1	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K4-425AXSP08	124.6	194.4	148.5	167	-	124.8	194.1	148.6	167	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K4-432AXSP08	115.7	181.7	138.3	155.9	-	115.9	181.4	138.3	155.6	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K4-525AXSP08	135.5	209	160.8	180.2	-	135.8	208.6	160.7	180	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K4-532AXSP08	127.8	198.6	152.1	170.8	-	127.9	198.2	152.1	170.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K5-425AXSP08	145.3	221.2	171.1	191.1	362.4	145.6	220.8	171.1	191	360.9	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K5-432AXSP08	138.6	213.5	164.4	184	352.9	139.1	213	164.2	183.8	351.1	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K5-425AXSP08	124.6	194.4	148.5	167	-	124.8	194.1	148.6	167	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K5-532AXSP08	115.7	181.7	138.3	155.9	-	115.9	181.4	138.3	155.6	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K5-625AXSP08	135.5	209	160.8	180.2	-	135.8	208.6	160.7	180	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K5-532AXSP08	127.8	198.6	152.1	170.8	-	127.9	198.2	152.1	170.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K5-625AXSP08	145.3	221.2	171.1	191.1	362.4	145.6	220.8	171.1	191	360.9	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K5-632AXSP08	138.6	213.5	164.4	184	352.9	139.1	213	164.2	183.8	351.1	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K8-425AXSP08	124.6	194.4	148.5	167	-	124.8	194.1	148.6	167	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K8-432AXSP08	115.7	181.7	138.3	155.9	-	115.9	181.4	138.3	155.6	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB370K8-525AXSP08	135.5	209	160.8	180.2	-	135.8	208.6	160.7	180	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K8-532AXSP08	127.8	198.6	152.1	170.8	-	127.9	198.2	152.1	170.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB370K8-625AXSP08	145.3	221.2	171.1	191.1	362.4	145.6	220.8	171.1	191	360.9	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB370K8-632AXSP08	138.6	213.5	164.4	184	352.9	139.1	213	164.2	183.8	351.1	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB400B3-425AXSP08	123.6	192.9	147.4	165.7	-	124.2	193	147.8	166.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB400B3-432AXSP08	115.5	181.3	138.1	155.6	-	115.9	181.3	138.3	155.6	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB400B3-525AXSP08	133.3	205.5	157.9	176.9	-	133.9	205.5	158.4	177.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB400B3-532AXSP08	126.6	196.7	150.7	169.2	-	127.1	196.8	151	169.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	304	15.1	4"	244	12.9	3"	365	21.2	4"
EAW-FD15S3ZB400B3-632AXSP08	136.3	209.7	161.3	180.8	345.9	136.7	209.5	161.6	180.9	345.3	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB400C3-425AXSP08	128	200.2	152.7	171.8	-	128.5	199.8	153	172.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB400C3-432AXSP08	119.1	187.3	142.7	160.8	-	119.6	187.2	142.8	160.7	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB400C3-525AXSP08	138.5	214	164.4	184.4	-	139.2	214.1	164.8	184.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB400C3-532AXSP08	131.3	204	156	175.6	-	131.6	204	156.2	175.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB400C3-625AXSP08	147.4	224.8	173.6	194.1	368.3	148.2	224.8	174.1	194.3	367.5	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB400C3-632AXSP08	141.8	218.2	167.9	188	360.9	142.4	218.2	168.1	188.3	360	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB400C9-425AXSP08	128	200.2	152.7	171.8	-	128.5	199.8	153	172.1	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB400C9-432AXSP08	119.1	187.3	142.7	160.8	-	119.6	187.2	142.8	160.7	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB400C9-525AXSP08	138.5	214	164.4	184.4	-	139.2	214.1	164.8	184.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB400C9-532AXSP08	131.3	204	156	175.6	-	131.6	204	156.2	175.5	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB400C9-625AXSP08	147.4	224.8	173.6	194.1	368.3	148.2	224.8	174.1	194.3	367.5	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB400C9-632AXSP08	141.8	218.2	167.9	188	360.9	142.4	218.2	168.1											

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3ZB550C3-632AXSP08	157.3	243	186.5	209.1	-	157.9	243.3	187	209.7	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C4-425AXSP06	137.4	217.9	165.2	186.6	-	138.6	218.3	166	187.2	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550C4-432AXSP08	131.1	207	157.2	177.4	-	131.8	206.9	157.6	177.5	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550C4-525AXSP08	153.8	238.6	182.9	205.3	-	154.9	239	183.5	205.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C4-532AXSP08	144.9	226.3	172.9	194.2	-	145.6	226.2	173.1	194.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C4-625AXSP08	164.3	251.7	194	217.2	-	165.4	251.9	194.7	217.6	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C4-632AXSP08	157.3	243	186.5	209.1	-	157.9	243.3	187	209.7	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C5-425AXSP06	137.4	217.9	165.2	186.6	-	138.6	218.3	166	187.2	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550C5-432AXSP08	131.1	207	157.2	177.4	-	131.8	206.9	157.6	177.5	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550C5-425AXSP08	153.8	238.6	182.9	205.3	-	154.9	239	183.5	205.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C5-532AXSP08	144.9	226.3	172.9	194.2	-	145.6	226.2	173.1	194.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C5-625AXSP08	164.3	251.7	194	217.2	-	165.4	251.9	194.7	217.6	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C5-632AXSP08	157.3	243	186.5	209.1	-	157.9	243.3	187	209.7	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C8-425AXSP06	137.4	217.9	165.2	186.6	-	138.6	218.3	166	187.2	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550C8-432AXSP08	131.1	207	157.2	177.4	-	131.8	206.9	157.6	177.5	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550C8-525AXSP08	153.8	238.6	182.9	205.3	-	154.9	239	183.5	205.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C8-532AXSP08	144.9	226.3	172.9	194.2	-	145.6	226.2	173.1	194.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C8-625AXSP08	164.3	251.7	194	217.2	-	165.4	251.9	194.7	217.6	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C8-632AXSP08	157.3	243	186.5	209.1	-	157.9	243.3	187	209.7	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C9-425AXSP06	137.4	217.9	165.2	186.6	-	138.6	218.3	166	187.2	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550C9-432AXSP08	131.1	207	157.2	177.4	-	131.8	206.9	157.6	177.5	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550C9-532AXSP08	144.9	226.3	172.9	194.2	-	145.6	226.2	173.1	194.7	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550C9-625AXSP08	164.3	251.7	194	217.2	-	165.4	251.9	194.7	217.6	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550C9-632AXSP08	157.3	243	186.5	209.1	-	157.9	243.3	187	209.7	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K2-425AXSP06	131.6	208.5	158.3	178.5	-	132.6	208.6	159	179.1	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550K2-432AXSP08	125.9	198.5	150.8	170.1	-	126.4	198.2	151	170.2	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550K2-525AXSP08	147.9	228.9	175.8	197.2	-	148.6	228.8	175.9	197.1	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K2-532AXSP08	139.1	217	165.8	186.5	-	139.6	216.6	166.1	186.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K2-625AXSP06	158.7	242.3	187	209.3	-	159.3	242.3	187.5	209.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K2-632AXSP08	151.3	233.7	179.3	201	-	151.9	233.4	179.7	201.1	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K3-425AXSP06	131.6	208.5	158.3	178.5	-	132.6	208.6	159	179.1	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550K3-432AXSP08	125.9	198.5	150.8	170.1	-	126.4	198.2	151	170.2	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550K3-525AXSP08	147.9	228.9	175.8	197.2	-	148.6	228.8	175.9	197.1	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K3-532AXSP08	139.1	217	165.8	186.5	-	139.6	216.6	166.1	186.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K3-625AXSP06	158.7	242.3	187	209.3	-	159.3	242.3	187.5	209.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K3-632AXSP08	151.3	233.7	179.3	201	-	151.9	233.4	179.7	201.1	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K4-425AXSP06	131.6	208.5	158.3	178.5	-	132.6	208.6	159	179.1	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550K4-432AXSP08	125.9	198.5	150.8	170.1	-	126.4	198.2	151	170.2	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550K4-525AXSP08	147.9	228.9	175.8	197.2	-	148.6	228.8	175.9	197.1	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K4-532AXSP08	139.1	217	165.8	186.5	-	139.6	216.6	166.1	186.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K4-625AXSP06	158.7	242.3	187	209.3	-	159.3	242.3	187.5	209.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K4-632AXSP08	151.3	233.7	179.3	201	-	151.9	233.4	179.7	201.1	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K5-425AXSP06	131.6	208.5	158.3	178.5	-	132.6	208.6	159	179.1	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550K5-432AXSP08	125.9	198.5	150.8	170.1	-	126.4	198.2	151	170.2	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550K5-525AXSP08	147.9	228.9	175.8	197.2	-	148.6	228.8	175.9	197.1	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K5-532AXSP08	139.1	217	165.8	186.5	-	139.6	216.6	166.1	186.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K5-625AXSP06	158.7	242.3	187	209.3	-	159.3	242.3	187.5	209.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K5-632AXSP08	151.3	233.7	179.3	201	-	151.9	233.4	179.7	201.1	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K8-425AXSP06	131.6	208.5	158.3	178.5	-	132.6	208.6	159	179.1	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550K8-432AXSP08	125.9	198.5	150.8	170.1	-	126.4	198.2	151	170.2	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550K8-525AXSP06	147.9	228.9	175.8	197.2	-	148.6	228.8	175.9	197.1	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K8-532AXSP08	139.1	217	165.8	186.5	-	139.6	216.6	166.1	186.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K8-625AXSP06	158.7	242.3	187	209.3	-	159.3	242.3	187.5	209.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K8-632AXSP08	151.3	233.7	179.3	201	-	151.9	233.4	179.7	201.1	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K9-425AXSP06	131.6	208.5	158.3	178.5	-	132.6	208.6	159	179.1	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550K9-432AXSP08	125.9	198.5	150.8	170.1	-	126.4	198.2	151	170.2	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550K9-525AXSP06	147.9	228.9	175.8	197.2	-	148.6	228.8	175.9	197.1	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K9-532AXSP08	139.1	217	165.8	186.5	-	139.6	216.6	166.1	186.4	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550K9-625AXSP06	158.7	242.3	187	209.3	-	159.3	242.3	187.5	209.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550K9-632AXSP08	151.3	233.7	179.3	201	-	151.9	233.4	179.7	201.1	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550R3-425AXSP06	134.2	212.3	161.3	181.9	-	135.2	212.9	162.1	182.7	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD15S3ZB550R3-432AXSP08	128.2	202	153.8	173.4	-	128.8	202.3	154	173.5	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD15S3ZB550R3-525AXSP06	150.7	233.4	179.1	201	-	151.4	233.4	179.3	200.9	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550R3-532AXSP08	141.6	220.9	168.9	190	-	142.2	220.9	169.2	190	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD15S3ZB550R3-625AXSP06	161.4	247.1	190.6	213	-	162.1	246.8	190.9	213.3	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB550R3-632AXSP08	154	238	182.8	205	-	154.7	238	183.1	204.9	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD15S3ZB750K2-425AXSP06	139	220.1	167.1	1															

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZB750K9-625AXSP08	166.5	254.9	196.6	219.9	-	167.2	255.3	197.2	220.5	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD1553ZB750K9-632AXSP08	159.1	245.9	188.6	211.6	-	159.8	245.9	189.2	212.2	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD1553ZB750R3-425AXSP06	136.2	215.8	163.7	184.8	-	137.3	216.2	164.4	185.4	-	203	15.9	3"	162	10.5	3"	244	22.4	3"
EAW-FD1553ZB750R3-432AXSP08	130.2	205.5	156.1	176.1	-	130.8	205.6	156.5	176.4	-	152	18.9	3"	122	12.5	3"	183	26.6	3"
EAW-FD1553ZB750R3-525AXSP08	152.6	236.5	181.4	203.3	-	153.3	236.6	181.7	203.9	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD1553ZB750R3-532AXSP08	143.6	224.2	171.3	192.8	-	144.3	224.4	171.8	192.9	-	186	19.8	3"	149	13	3"	223	27.8	3"
EAW-FD1553ZB750R3-625AXSP08	163	249.7	192.5	215.5	-	163.9	249.6	193	215.7	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD1553ZB750R3-632AXSP08	155.8	240.6	185	207.5	-	156.7	240.8	185.5	207.6	-	225	21	3"	180	13.8	3"	270	25.9	4"
EAW-FD1553ZK370C2-425AXSP06	134.8	211.4	161.1	181.6	-	135.3	211.4	161.4	181.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370C2-432AXSP08	128.5	201.2	153.5	172.8	-	128.7	200.5	153.4	172.5	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370C2-525AXSP08	150.5	231.3	178	199.2	-	150.7	230.9	178	199.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C2-532AXSP08	141.9	220	168.6	189.3	-	142.1	219.6	168.6	189.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C2-625AXSP08	160.5	243.7	188.7	210.6	-	160.9	243.2	188.8	210.7	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C2-632AXSP08	154	236.2	182	203.7	-	154.3	235.4	181.9	203.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C4-425AXSP06	134.8	211.4	161.1	181.6	-	135.3	211.4	161.4	181.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370C4-432AXSP08	128.5	201.2	153.5	172.8	-	128.7	200.5	153.4	172.5	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370C4-525AXSP08	150.5	231.3	178	199.2	-	150.7	230.9	178	199.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C4-532AXSP08	141.9	220	168.6	189.3	-	142.1	219.6	168.6	189.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C4-625AXSP08	160.5	243.7	188.7	210.6	-	160.9	243.2	188.8	210.7	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C4-632AXSP08	154	236.2	182	203.7	-	154.3	235.4	181.9	203.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C5-425AXSP06	134.8	211.4	161.1	181.6	-	135.3	211.4	161.4	181.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370C5-432AXSP08	128.5	201.2	153.5	172.8	-	128.7	200.5	153.4	172.5	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370C5-525AXSP08	150.5	231.3	178	199.2	-	150.7	230.9	178	199.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C5-532AXSP08	141.9	220	168.6	189.3	-	142.1	219.6	168.6	189.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C5-625AXSP08	160.5	243.7	188.7	210.6	-	160.9	243.2	188.8	210.7	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C5-632AXSP08	154	236.2	182	203.7	-	154.3	235.4	181.9	203.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C8-425AXSP06	134.8	211.4	161.1	181.6	-	135.3	211.4	161.4	181.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370C8-432AXSP08	128.5	201.2	153.5	172.8	-	128.7	200.5	153.4	172.5	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370C8-525AXSP08	150.5	231.3	178	199.2	-	150.7	230.9	178	199.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C8-532AXSP08	141.9	220	168.6	189.3	-	142.1	219.6	168.6	189.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370C8-625AXSP08	160.5	243.7	188.7	210.6	-	160.9	243.2	188.8	210.7	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370C8-632AXSP08	154	236.2	182	203.7	-	154.3	235.4	181.9	203.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K2-425AXSP06	130.4	204.5	156.1	175.5	-	130.7	204.2	156.1	175.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370K2-432AXSP08	124.3	194.4	148.4	167.1	-	124.5	193.9	148.3	166.6	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370K2-525AXSP08	146.1	224.5	172.7	193.4	-	146.3	223.8	172.7	193.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K2-532AXSP08	137.6	212.9	163.4	183.3	-	137.8	212.1	163	182.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K2-625AXSP08	156.7	237.8	184.2	205.6	-	157	237	183.8	205.1	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K2-632AXSP08	149.8	229.2	176.7	197.8	-	149.9	228.3	176.6	197.3	375.4	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K4-425AXSP06	130.4	204.5	156.1	175.5	-	130.7	204.2	156.1	175.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370K4-432AXSP08	124.3	194.4	148.4	167.1	-	124.5	193.9	148.3	166.6	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370K4-525AXSP08	146.1	224.5	172.7	193.4	-	146.3	223.8	172.7	193.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K4-532AXSP08	137.6	212.9	163.4	183.3	-	137.8	212.1	163	182.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K4-625AXSP08	156.7	237.8	184.2	205.6	-	157	237	183.8	205.1	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K4-632AXSP08	149.8	229.2	176.7	197.8	-	149.9	228.3	176.6	197.3	375.4	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K5-425AXSP06	130.4	204.5	156.1	175.5	-	130.7	204.2	156.1	175.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370K5-432AXSP08	124.3	194.4	148.4	167.1	-	124.5	193.9	148.3	166.6	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370K5-525AXSP08	146.1	224.5	172.7	193.4	-	146.3	223.8	172.7	193.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K5-532AXSP08	137.6	212.9	163.4	183.3	-	137.8	212.1	163	182.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K5-625AXSP08	156.7	237.8	184.2	205.6	-	157	237	183.8	205.1	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K5-632AXSP08	149.8	229.2	176.7	197.8	-	149.9	228.3	176.6	197.3	375.4	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K8-425AXSP06	130.4	204.5	156.1	175.5	-	130.7	204.2	156.1	175.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK370K8-432AXSP08	124.3	194.4	148.4	167.1	-	124.5	193.9	148.3	166.6	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK370K8-525AXSP08	146.1	224.5	172.7	193.4	-	146.3	223.8	172.7	193.1	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K8-532AXSP08	137.6	212.9	163.4	183.3	-	137.8	212.1	163	182.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK370K8-625AXSP08	156.7	237.8	184.2	205.6	-	157	237	183.8	205.1	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK370K8-632AXSP08	149.8	229.2	176.7	197.8	-	149.9	228.3	176.6	197.3	375.4	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK400B3-425AXSP06	130.3	204.3	155.9	175.5	-	130.8	204.4	156.3	175.6	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK400B3-432AXSP08	124.8	195.2	149	167.8	-	125.1	194.8	149	167.4	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK400B3-525AXSP08	144.8	222.5	171.2	191.7	-	145.4	222	171.3	191.8	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK400B3-532AXSP08	137.3	212.4	163	182.9	-	137.5	212	163	182.8	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK400B3-625AXSP08	154	233.3	180.8	201.7	-	154.4	233	181	201.7	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK400B3-632AXSP08	148.4	226.9	175.1	195.9	374	148.9	226.7	175.1	195.9	372.6	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK400C3-425AXSP06	134.8	211.4	161.1	181.6	-	135.3	211.4	161.4	181.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK400C3-432AXSP08	128.5	201.2	153.5	172.8	-	128.7	200.5	153.4	172.5	-	152	20.7	3"	122	13.6	3"	183	29	3"
EAW-FD1553ZK400C3-525AXSP08	150.5	231.3	178	199.2	-	150.7	230.9	178	199.1	-	186	21.5	3"	149	14.2	3"	2		

EAW-FD15S3ZK550C2-532AXSP08	157	244.5	187.2	210.1	-	157.4	244.3	187	210.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550C2-625AXSP08	179.4	273.5	211.4	236.2	-	179.9	273.2	211.7	236.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C2-632AXSP08	171.1	263.3	202.7	226.9	-	171.7	263.1	202.6	227	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C3-425AXSP06	149.2	235.1	178.9	201.6	-	149.9	235	179.1	201.9	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C3-432AXSP06	138	218.6	165.8	187.4	-	138.5	218.5	166.2	187.4	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C3-525AXSP06	165.1	257.3	196.8	220.9	-	166.1	257.3	197.4	221.5	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD15S3ZK550C3-532AXSP08	157	244.5	187.2	210.1	-	157.4	244.3	187	210.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550C3-625AXSP08	179.4	273.5	211.4	236.2	-	179.9	273.2	211.7	236.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C3-632AXSP08	171.1	263.3	202.7	226.9	-	171.7	263.1	202.6	227	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C4-425AXSP06	149.2	235.1	178.9	201.6	-	149.9	235	179.1	201.9	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C4-432AXSP06	138	218.6	165.8	187.4	-	138.5	218.5	166.2	187.4	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C4-525AXSP06	165.1	257.3	196.8	220.9	-	166.1	257.3	197.4	221.5	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD15S3ZK550C4-532AXSP08	157	244.5	187.2	210.1	-	157.4	244.3	187	210.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550C5-425AXSP06	179.4	273.5	211.4	236.2	-	179.9	273.2	211.7	236.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C5-632AXSP08	171.1	263.3	202.7	226.9	-	171.7	263.1	202.6	227	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C8-425AXSP06	149.2	235.1	178.9	201.6	-	149.9	235	179.1	201.9	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C8-432AXSP06	138	218.6	165.8	187.4	-	138.5	218.5	166.2	187.4	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C8-525AXSP06	165.1	257.3	196.8	220.9	-	166.1	257.3	197.4	221.5	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD15S3ZK550C8-532AXSP08	157	244.5	187.2	210.1	-	157.4	244.3	187	210.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550C8-625AXSP08	179.4	273.5	211.4	236.2	-	179.9	273.2	211.7	236.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C8-632AXSP08	171.1	263.3	202.7	226.9	-	171.7	263.1	202.6	227	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C9-425AXSP06	149.2	235.1	178.9	201.6	-	149.9	235	179.1	201.9	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C9-432AXSP06	138	218.6	165.8	187.4	-	138.5	218.5	166.2	187.4	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550C9-525AXSP06	165.1	257.3	196.8	220.9	-	166.1	257.3	197.4	221.5	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD15S3ZK550C9-532AXSP08	157	244.5	187.2	210.1	-	157.4	244.3	187	210.2	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550C9-625AXSP08	179.4	273.5	211.4	236.2	-	179.9	273.2	211.7	236.2	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550C9-632AXSP08	171.1	263.3	202.7	226.9	-	171.7	263.1	202.6	227	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K2-425AXSP06	142.8	224.9	171.2	192.8	-	143.5	224.6	171.3	192.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K2-432AXSP06	132.1	209.2	158.9	179.4	-	132.8	209.4	159.2	179.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K2-525AXSP08	160.1	246.8	189.8	212.5	-	160.3	246.4	189.8	212.4	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K2-532AXSP08	150.4	233.5	178.8	200.9	-	150.7	233.2	178.8	200.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K2-625AXSP08	172	261.9	202.4	226.1	-	172.4	261	202.5	225.9	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K2-632AXSP08	163.9	251.8	193.8	217.2	-	164.3	251.2	193.7	216.6	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K3-425AXSP06	142.8	224.9	171.2	192.8	-	143.5	224.6	171.3	192.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K3-432AXSP06	132.1	209.2	158.9	179.4	-	132.8	209.4	159.2	179.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K3-525AXSP08	160.1	246.8	189.8	212.5	-	160.3	246.4	189.8	212.4	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K3-532AXSP08	150.4	233.5	178.8	200.9	-	150.7	233.2	178.8	200.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K3-625AXSP08	172	261.9	202.4	226.1	-	172.4	261	202.5	225.9	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K3-632AXSP08	163.9	251.8	193.8	217.2	-	164.3	251.2	193.7	216.6	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K4-425AXSP06	142.8	224.9	171.2	192.8	-	143.5	224.6	171.3	192.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K4-432AXSP06	132.1	209.2	158.9	179.4	-	132.8	209.4	159.2	179.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K4-525AXSP08	160.1	246.8	189.8	212.5	-	160.3	246.4	189.8	212.4	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K4-532AXSP08	150.4	233.5	178.8	200.9	-	150.7	233.2	178.8	200.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K4-625AXSP08	172	261.9	202.4	226.1	-	172.4	261	202.5	225.9	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K4-632AXSP08	163.9	251.8	193.8	217.2	-	164.3	251.2	193.7	216.6	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K5-425AXSP06	142.8	224.9	171.2	192.8	-	143.5	224.6	171.3	192.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K5-432AXSP06	132.1	209.2	158.9	179.4	-	132.8	209.4	159.2	179.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K5-525AXSP08	160.1	246.8	189.8	212.5	-	160.3	246.4	189.8	212.4	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K5-532AXSP08	150.4	233.5	178.8	200.9	-	150.7	233.2	178.8	200.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K5-625AXSP08	172	261.9	202.4	226.1	-	172.4	261	202.5	225.9	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K5-632AXSP08	163.9	251.8	193.8	217.2	-	164.3	251.2	193.7	216.6	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K8-425AXSP06	142.8	224.9	171.2	192.8	-	143.5	224.6	171.3	192.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K8-432AXSP06	132.1	209.2	158.9	179.4	-	132.8	209.4	159.2	179.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K8-525AXSP08	160.1	246.8	189.8	212.5	-	160.3	246.4	189.8	212.4	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K8-532AXSP08	150.4	233.5	178.8	200.9	-	150.7	233.2	178.8	200.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K8-625AXSP08	172	261.9	202.4	226.1	-	172.4	261	202.5	225.9	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K8-632AXSP08	163.9	251.8	193.8	217.2	-	164.3	251.2	193.7	216.6	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K9-425AXSP06	142.8	224.9	171.2	192.8	-	143.5	224.6	171.3	192.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K9-432AXSP06	132.1	209.2	158.9	179.4	-	132.8	209.4	159.2	179.5	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550K9-525AXSP08	160.1	246.8	189.8	212.5	-	160.3	246.4	189.8	212.4	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K9-532AXSP08	150.4	233.5	178.8	200.9	-	150.7	233.2	178.8	200.9	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD15S3ZK550K9-625AXSP08	172	261.9	202.4	226.1	-	172.4	261	202.5	225.9	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550K9-632AXSP08	163.9	251.8	193.8	217.2	-	164.3	251.2	193.7	216.6	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD15S3ZK550R3-425AXSP06	145.6	229.4	174.4	196.8	-	146.5	229.3	175	197.1	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550R3-432AXSP06	134.9	213.8	162	183	-	135.5	213.7	162.5	183.2	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD15S3ZK550R3-525AXSP08	163.4	251.6	193.4	216.9	-	163.7	251.3	193.4	21										

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZK750K4-625AXSP08	181.6	277.1	214.1	239.2	-	182.2	276.9	214.5	239.3	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K4-632AXSP08	173.1	266.6	204.9	229.7	-	173.5	266.1	205	229.8	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K5-425AXSP08	151.2	238.3	181.2	204.3	-	152.1	238.5	182	204.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750K5-432AXSP06	140.2	222.4	168.5	190.3	-	140.9	222.5	168.9	190.7	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750K5-525AXSP06	167.1	260.3	199.3	223.7	-	168.2	260.6	199.9	224.4	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD1553ZK750K5-532AXSP08	159	247.4	189.3	212.9	-	159.6	247.5	189.6	212.8	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK750K5-625AXSP08	181.6	277.1	214.1	239.2	-	182.2	276.9	214.5	239.3	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K5-632AXSP08	173.1	266.6	204.9	229.7	-	173.5	266.1	205	229.8	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K8-425AXSP06	151.2	238.3	181.2	204.3	-	152.1	238.5	182	204.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750K8-432AXSP06	140.2	222.4	168.5	190.3	-	140.9	222.5	168.9	190.7	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750K8-525AXSP06	167.1	260.3	199.3	223.7	-	168.2	260.6	199.9	224.4	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD1553ZK750K8-532AXSP08	159	247.4	189.3	212.9	-	159.6	247.5	189.6	212.8	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK750K8-625AXSP08	181.6	277.1	214.1	239.2	-	182.2	276.9	214.5	239.3	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K8-632AXSP08	173.1	266.6	204.9	229.7	-	173.5	266.1	205	229.8	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K9-425AXSP06	151.2	238.3	181.2	204.3	-	152.1	238.5	182	204.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750K9-432AXSP06	140.2	222.4	168.5	190.3	-	140.9	222.5	168.9	190.7	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750K9-525AXSP06	167.1	260.3	199.3	223.7	-	168.2	260.6	199.9	224.4	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD1553ZK750K9-532AXSP08	159	247.4	189.3	212.9	-	159.6	247.5	189.6	212.8	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK750K9-625AXSP08	181.6	277.1	214.1	239.2	-	182.2	276.9	214.5	239.3	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750K9-632AXSP08	173.1	266.6	204.9	229.7	-	173.5	266.1	205	229.8	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750R3-425AXSP06	148.2	233.4	177.6	200.2	-	149	233.6	178.1	200.6	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750R3-432AXSP06	137.4	217.7	165.3	186.6	-	138.1	217.8	165.7	186.8	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1553ZK750R3-525AXSP06	163.5	254.7	194.9	219.1	-	164.5	255	195.5	219.3	-	254	18.9	3"	203	12.4	3"	304	22.1	4"
EAW-FD1553ZK750R3-532AXSP08	156	242.4	185.6	208.3	-	156.2	242.3	185.6	208.6	-	186	21.5	3"	149	14.2	3"	223	30.2	3"
EAW-FD1553ZK750R3-625AXSP08	177.5	270.6	209.2	233.8	-	178.3	270.7	209.5	234.1	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1553ZK750R3-632AXSP08	169.7	261.1	200.8	225	-	170	260.5	200.9	224.7	-	225	22.7	3"	180	14.9	3"	270	28.3	4"
EAW-FD1554PB370C2-425AXSP04	148.4	237.7	180	203.4	403.3	150.1	238.4	181.3	204.3	403.6	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD1554PB370C2-432AXSP06	146	229.7	174.8	197.2	-	146.6	229.8	175.3	197.5	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370C2-525AXSP06	170.9	264	202.8	227.4	-	171.9	264.4	203.4	228	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C2-532AXSP06	162.3	252.8	193.3	217.2	-	163.1	252.9	194	217.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C2-625AXSP06	179.7	273.9	211.7	236.8	449.5	180.8	274.5	212.8	237.6	449.5	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C2-632AXSP06	173.4	267.5	205.6	230.4	442.6	174.5	267.7	206.4	230.8	441.8	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C4-425AXSP04	148.4	237.7	180	203.4	403.3	150.1	238.4	181.3	204.3	403.6	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD1554PB370C4-432AXSP06	146	229.7	174.8	197.2	-	146.6	229.8	175.3	197.5	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370C4-525AXSP06	170.9	264	202.8	227.4	-	171.9	264.4	203.4	228	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C4-532AXSP06	162.3	252.8	193.3	217.2	-	163.1	252.9	194	217.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C4-625AXSP06	179.7	273.9	211.7	236.8	449.5	180.8	274.5	212.8	237.6	449.5	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C4-632AXSP06	173.4	267.5	205.6	230.4	442.6	174.5	267.7	206.4	230.8	441.8	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C5-425AXSP04	148.4	237.7	180	203.4	403.3	150.1	238.4	181.3	204.3	403.6	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD1554PB370C5-432AXSP06	146	229.7	174.8	197.2	-	146.6	229.8	175.3	197.5	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370C5-525AXSP06	170.9	264	202.8	227.4	-	171.9	264.4	203.4	228	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C5-532AXSP06	162.3	252.8	193.3	217.2	-	163.1	252.9	194	217.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C5-625AXSP06	179.7	273.9	211.7	236.8	449.5	180.8	274.5	212.8	237.6	449.5	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C5-632AXSP06	173.4	267.5	205.6	230.4	442.6	174.5	267.7	206.4	230.8	441.8	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C8-425AXSP04	148.4	237.7	180	203.4	403.3	150.1	238.4	181.3	204.3	403.6	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD1554PB370C8-432AXSP06	146	229.7	174.8	197.2	-	146.6	229.8	175.3	197.5	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370C8-432AXSP06	146	229.7	174.8	197.2	-	146.6	229.8	175.3	197.5	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370C8-525AXSP06	170.9	264	202.8	227.4	-	171.9	264.4	203.4	228	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C8-532AXSP06	162.3	252.8	193.3	217.2	-	163.1	252.9	194	217.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370C8-625AXSP06	179.7	273.9	211.7	236.8	449.5	180.8	274.5	212.8	237.6	449.5	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370C8-632AXSP06	173.4	267.5	205.6	230.4	442.6	174.5	267.7	206.4	230.8	441.8	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370K2-425AXSP06	153.1	239.3	182.7	205.6	-	153.7	239.2	183	205.9	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370K2-432AXSP06	142.3	224.1	170.4	192.1	-	142.8	223.7	170.7	192	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370K2-525AXSP06	168.6	260.3	200.1	224.3	-	169.3	260.2	200.3	224.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370K2-532AXSP06	159.1	247.6	189.5	212.8	-	159.8	247.4	189.6	212.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370K2-625AXSP06	179.1	273.3	211.3	236	448	180	273.2	211.5	236.1	446.6	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370K2-632AXSP06	171.4	264.3	203.3	227.7	437.2	172	264.1	203.4	227.8	435.6	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370K4-425AXSP06	153.1	239.3	182.7	205.6	-	153.7	239.2	183	205.9	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370K4-432AXSP06	142.3	224.1	170.4	192.1	-	142.8	223.7	170.7	192	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370K4-525AXSP06	168.6	260.3	200.1	224.3	-	169.3	260.2	200.3	224.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370K4-532AXSP06	159.1	247.6	189.5	212.8	-	159.8	247.4	189.6	212.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD1554PB370K4-625AXSP06	179.1	273.3	211.3	236	448	180	273.2	211.5	236.1	446.6	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370K4-632AXSP06	171.4	264.3	203.3	227.7	437.2	172	264.1	203.4	227.8	435.6	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD1554PB370K5-425AXSP06	153.1	239.3	182.7	205.6	-	153.7	239.2	183	205.9	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD1554PB370K5-432AXSP06	142.3	224.1	170.4	192.1	-														

EAW-FD15S4PB400K9-532AXSP06	159.1	247.6	189.5	212.8	-	159.8	247.4	189.6	212.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB400K9-625AXSP06	179.1	273.3	211.3	236	448	180	273.2	211.5	236.1	446.6	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB400K9-632AXSP06	171.4	264.3	203.3	227.7	437.2	172	264.1	203.4	227.8	435.6	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB400R3-425AXSP06	154.7	241.8	184.6	207.8	-	155.3	241.9	184.9	208.1	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB400R3-432AXSP06	143.9	226.6	172.2	194.2	-	144.4	226.3	172.5	194.2	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB400R3-525AXSP06	170.3	263	201.8	226.6	-	171.1	263	202.4	226.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB400R3-532AXSP06	160.9	250.1	191.6	215.3	-	161.4	250	191.9	215.1	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB400R3-625AXSP06	180.8	275.9	213.3	238.2	-	181.4	275.8	213.5	238.4	451.1	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB400R3-632AXSP06	173	266.6	204.9	229.9	441.1	173.7	266.4	205.5	229.8	440.2	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550R3-425AXSP04	153.2	245.3	185.5	209.6	416.9	155.1	246.5	187.1	211.1	417.4	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550R3-432AXSP06	151	238.2	180.9	204	-	152	238.4	181.7	204.6	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB550R3-525AXSP04	-	-	-	-	-	-	-	-	-	-	338	13.8	4"	270	9.1	4"	406	19.5	4"
EAW-FD15S4PB550R3-532AXSP06	-	-	-	-	-	168.1	261.1	200	224.4	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550R3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	15	4"	325	9.9	4"	487	17	(2) 4"
EAW-FD15S4PB550R3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	15	4"	325	9.9	4"	487	17	(2) 4"
EAW-FD15S4PB550C2-425AXSP04	164	262.6	198.6	224.8	448.1	166	264.3	200.3	226.2	448.3	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C2-432AXSP04	151.8	245.3	185	209.4	420.4	153.6	246.3	186.2	210.7	420.9	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C2-525AXSP06	189.3	293.7	225.1	252.7	-	190.6	294.4	226.3	253.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C2-532AXSP06	179	279.7	213.6	240	-	179.9	280.1	214.2	240.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C2-632AXSP06	-	-	-	-	-	193.3	297.5	228.9	256.3	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550C3-425AXSP04	164	262.6	198.6	224.8	448.1	166	264.3	200.3	226.2	448.3	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C3-432AXSP04	151.8	245.3	185	209.4	420.4	153.6	246.3	186.2	210.7	420.9	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C3-525AXSP06	189.3	293.7	225.1	252.7	-	190.6	294.4	226.3	253.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C3-532AXSP06	179	279.7	213.6	240	-	179.9	280.1	214.2	240.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	15	4"	325	9.9	4"	487	17	(2) 4"
EAW-FD15S4PB550C3-632AXSP06	-	-	-	-	-	193.3	297.5	228.9	256.3	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550C4-425AXSP04	164	262.6	198.6	224.8	448.1	166	264.3	200.3	226.2	448.3	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C4-432AXSP04	151.8	245.3	185	209.4	420.4	153.6	246.3	186.2	210.7	420.9	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C4-525AXSP06	189.3	293.7	225.1	252.7	-	190.6	294.4	226.3	253.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C4-532AXSP06	179	279.7	213.6	240	-	179.9	280.1	214.2	240.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C4-632AXSP06	-	-	-	-	-	193.3	297.5	228.9	256.3	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550C5-425AXSP04	164	262.6	198.6	224.8	448.1	166	264.3	200.3	226.2	448.3	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C5-432AXSP04	151.8	245.3	185	209.4	420.4	153.6	246.3	186.2	210.7	420.9	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C5-525AXSP06	189.3	293.7	225.1	252.7	-	190.6	294.4	226.3	253.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C5-632AXSP06	179	279.7	213.6	240	-	179.9	280.1	214.2	240.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C6-425AXSP04	164	262.6	198.6	224.8	448.1	166	264.3	200.3	226.2	448.3	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C6-432AXSP04	151.8	245.3	185	209.4	420.4	153.6	246.3	186.2	210.7	420.9	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550C6-525AXSP06	189.3	293.7	225.1	252.7	-	190.6	294.4	226.3	253.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C6-532AXSP06	179	279.7	213.6	240	-	179.9	280.1	214.2	240.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550C6-632AXSP06	-	-	-	-	-	193.3	297.5	228.9	256.3	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-425AXSP04	157.9	252.7	191.3	216.1	430.2	159.5	253.6	192.5	217.3	430	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550K9-432AXSP06	154.3	243.1	185	208.4	-	155	243.6	185.4	208.8	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB550K9-525AXSP06	183.1	283.5	217.6	244.2	-	184.2	283.9	218.2	244.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-532AXSP06	172.6	269.5	205.8	231.5	-	173.3	269.8	206.3	232	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-625AXSP06	194.7	298.1	229.8	257.3	-	195.7	297.9	230.4	257.5	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-632AXSP06	186	287.5	220.8	247.6	-	187	287.3	221.3	247.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-425AXSP04	157.9	252.7	191.3	216.1	430.2	159.5	253.6	192.5	217.3	430	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550K9-432AXSP06	154.3	243.1	185	208.4	-	155	243.6	185.4	208.8	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB550K9-525AXSP06	183.1	283.5	217.6	244.2	-	184.2	283.9	218.2	244.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-532AXSP06	172.6	269.5	205.8	231.5	-	173.3	269.8	206.3	232	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-625AXSP06	194.7	298.1	229.8	257.3	-	195.7	297.9	230.4	257.5	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-632AXSP06	186	287.5	220.8	247.6	-	187	287.3	221.3	247.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-425AXSP04	157.9	252.7	191.3	216.1	430.2	159.5	253.6	192.5	217.3	430	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550K9-432AXSP06	154.3	243.1	185	208.4	-	155	243.6	185.4	208.8	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB550K9-525AXSP06	183.1	283.5	217.6	244.2	-	184.2	283.9	218.2	244.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-532AXSP06	172.6	269.5	205.8	231.5	-	173.3	269.8	206.3	232	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-625AXSP06	194.7	298.1	229.8	257.3	-	195.7	297.9	230.4	257.5	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-632AXSP06	186	287.5	220.8	247.6	-	187	287.3	221.3	247.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-425AXSP04	157.9	252.7	191.3	216.1	430.2	159.5	253.6	192.5	217.3	430	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550K9-432AXSP06	154.3	243.1	185	208.4	-	155	243.6	185.4	208.8	-	180	19.1	3"	144	12.6	3"	216	26.9	3"
EAW-FD15S4PB550K9-525AXSP06	183.1	283.5	217.6	244.2	-	184.2	283.9	218.2	244.5	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-532AXSP06	172.6	269.5	205.8	231.5	-	173.3	269.8	206.3	232	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB550K9-625AXSP06	194.7	298.1	229.8	257.3	-	195.7	297.9	230.4	257.5	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-632AXSP06	186	287.5	220.8	247.6	-	187	287.3	221.3	247.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB550K9-425AXSP04	157.9	252.7	191.3	216.1	430.2	159.5	253.6	192.5	217.3	430	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB550K9-432AXSP06	154.3	243.1	185	208.4	-	155	243.6	185.4	208.8	-	180	19.1	3"	144	12.6	3"	216	26.9	

EAW-FD15S4PB750K4-425AXSP04	166	265.6	201	227.2	-	168	266.9	202.6	228.8	-	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K4-432AXSP04	153.4	247.9	186.8	211.8	425.2	155.3	249	188.1	212.9	425	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K4-525AXSP06	191.8	297.3	228.1	256.2	-	193	298.2	228.8	256.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K4-532AXSP06	180.9	282.9	215.9	242.6	-	181.8	283.3	216.6	243.3	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K4-625AXSP06	203.3	311.9	240.5	268.9	-	204.7	312.6	241.4	270	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K4-632AXSP06	194.4	300.8	230.9	259.1	-	195.5	301.5	231.5	259.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K5-425AXSP04	166	265.6	201	227.2	-	168	266.9	202.6	228.8	-	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K5-432AXSP04	153.4	247.9	186.8	211.8	425.2	155.3	249	188.1	212.9	425	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K5-525AXSP06	191.8	297.3	228.1	256.2	-	193	298.2	228.8	256.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K5-532AXSP06	180.9	282.9	215.9	242.6	-	181.8	283.3	216.6	243.3	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K5-625AXSP06	203.3	311.9	240.5	268.9	-	204.7	312.6	241.4	270	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K5-632AXSP06	194.4	300.8	230.9	259.1	-	195.5	301.5	231.5	259.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K8-425AXSP04	166	265.6	201	227.2	-	168	266.9	202.6	228.8	-	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K8-432AXSP04	153.4	247.9	186.8	211.8	425.2	155.3	249	188.1	212.9	425	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K8-532AXSP06	191.8	297.3	228.1	256.2	-	193	298.2	228.8	256.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K8-625AXSP06	203.3	311.9	240.5	268.9	-	204.7	312.6	241.4	270	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K8-632AXSP06	194.4	300.8	230.9	259.1	-	195.5	301.5	231.5	259.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K9-425AXSP04	166	265.6	201	227.2	-	168	266.9	202.6	228.8	-	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K9-432AXSP04	153.4	247.9	186.8	211.8	425.2	155.3	249	188.1	212.9	425	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750K9-525AXSP06	191.8	297.3	228.1	256.2	-	193	298.2	228.8	256.9	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K9-532AXSP06	180.9	282.9	215.9	242.6	-	181.8	283.3	216.6	243.3	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750K9-625AXSP06	203.3	311.9	240.5	268.9	-	204.7	312.6	241.4	270	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750K9-632AXSP06	194.4	300.8	230.9	259.1	-	195.5	301.5	231.5	259.7	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750R3-425AXSP04	162.8	260.6	197	222.7	443.7	164.7	261.7	198.5	224	444.5	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750R3-432AXSP04	150.6	243.4	183.4	207.7	416.5	152.4	244.4	184.6	208.9	417	270	12.9	4"	216	10.8	3"	325	18.1	4"
EAW-FD15S4PB750R3-525AXSP06	188	291.6	223.5	251	-	189.1	291.9	224.5	251.6	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750R3-532AXSP06	177.5	277.1	211.7	238.2	-	178.3	277.5	212.3	238.8	-	225	20.4	3"	180	13.5	3"	270	25.2	4"
EAW-FD15S4PB750R3-625AXSP06	199.6	305.4	235.7	263.5	-	200.6	306.2	236.6	264.5	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4PB750R3-632AXSP06	190.7	294.8	226.5	254.1	-	192	295.4	227.3	254.5	-	270	18.5	4"	216	14.5	3"	325	26	4"
EAW-FD15S4B370C2-425AXSP06	170.1	266	203.3	228.3	-	171	266	203.3	228.6	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C2-432AXSP06	158.3	249.2	189.5	213.5	-	158.8	248.7	189.8	213.5	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C2-525AXSP06	186.8	288.3	221.4	248.1	-	187.5	288	221.8	248.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C2-532AXSP06	176.9	275.2	210.7	236.5	-	177.4	275	210.9	236.7	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C2-625AXSP06	197.3	300.5	232.4	259.5	492.2	198.4	300.9	233.1	260.2	491.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C2-632AXSP06	189.6	292.2	224.9	251.8	483.1	190.5	292.2	225.2	252.1	481.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C4-425AXSP06	170.1	266	203.3	228.3	-	171	266	203.3	228.6	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C4-432AXSP06	158.3	249.2	189.5	213.5	-	158.8	248.7	189.8	213.5	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C4-525AXSP06	186.8	288.3	221.4	248.1	-	187.5	288	221.8	248.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C4-625AXSP06	176.9	275.2	210.7	236.5	-	177.4	275	210.9	236.7	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C4-632AXSP06	197.3	300.5	232.4	259.5	492.2	198.4	300.9	233.1	260.2	491.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C4-632AXSP06	189.6	292.2	224.9	251.8	483.1	190.5	292.2	225.2	252.1	481.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C5-425AXSP06	170.1	266	203.3	228.3	-	171	266	203.3	228.6	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C5-432AXSP06	158.3	249.2	189.5	213.5	-	158.8	248.7	189.8	213.5	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C5-525AXSP06	186.8	288.3	221.4	248.1	-	187.5	288	221.8	248.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C5-532AXSP06	176.9	275.2	210.7	236.5	-	177.4	275	210.9	236.7	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C5-625AXSP06	197.3	300.5	232.4	259.5	492.2	198.4	300.9	233.1	260.2	491.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C5-632AXSP06	189.6	292.2	224.9	251.8	483.1	190.5	292.2	225.2	252.1	481.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C8-425AXSP06	170.1	266	203.3	228.3	-	171	266	203.3	228.6	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C8-432AXSP06	158.3	249.2	189.5	213.5	-	158.8	248.7	189.8	213.5	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370C8-525AXSP06	186.8	288.3	221.4	248.1	-	187.5	288	221.8	248.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C8-532AXSP06	176.9	275.2	210.7	236.5	-	177.4	275	210.9	236.7	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370C8-625AXSP06	197.3	300.5	232.4	259.5	492.2	198.4	300.9	233.1	260.2	491.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370C8-632AXSP06	189.6	292.2	224.9	251.8	483.1	190.5	292.2	225.2	252.1	481.8	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370K2-425AXSP06	165.5	258.3	197.3	221.9	-	165.8	257.9	197.4	221.9	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370K2-432AXSP06	153.7	241.4	183.8	207.1	-	154.1	241	183.9	207.1	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370K2-525AXSP06	182.7	281.5	216.4	242.4	-	183.1	280.9	216.3	242.2	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370K2-532AXSP06	172.2	267.4	204.9	230	-	172.7	266.8	204.9	229.9	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370K2-625AXSP06	194.3	296.1	229.2	255.8	484.9	195	295.6	229	255.7	482.9	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370K2-632AXSP06	185.7	285.9	220.2	246.5	472.4	186	285.2	219.9	246.2	469.9	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370K4-425AXSP06	165.5	258.3	197.3	221.9	-	165.8	257.9	197.4	221.9	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370K4-432AXSP06	153.7	241.4	183.8	207.1	-	154.1	241	183.9	207.1	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4B370K4-525AXSP06	182.7	281.5	216.4	242.4	-	183.1	280.9	216.3	242.2	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370K4-532AXSP06	172.2	267.4	204.9	230	-	172.7	266.8	204.9	229.9	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4B370K4-625AXSP06	194.3	296.1	229.2	255.8	484.9	195	295.6	229	255.7	482.9	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4B370K4-632AXSP06	185.7	285.9	220.2	246.5	472.4	186	285.2	219.9	246.2	469.9	304	19	4"	244	1				

EAW-FD15S4ZB400K3-632AXSP06	185.7	285.9	220.2	246.5	472.4	186	285.2	219.9	246.2	469.9	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB400K9-425AXSP06	165.5	258.3	197.3	221.9	-	165.8	257.9	197.4	221.9	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB400K9-432AXSP06	153.7	241.4	183.8	207.1	-	154.1	241	183.9	207.1	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB400K9-525AXSP06	182.7	281.5	216.4	242.4	-	183.1	280.9	216.3	242.2	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB400K9-532AXSP06	172.2	267.4	204.9	230	-	172.7	266.8	204.9	229.9	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB400K9-625AXSP06	194.3	296.1	229.2	255.8	484.9	195	295.6	229	255.7	482.9	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB400K9-632AXSP06	185.7	285.9	220.2	246.5	472.4	186	285.2	219.9	246.2	469.9	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB400R3-425AXSP06	167.4	261.6	199.7	224.6	-	167.9	261.3	199.8	224.7	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB400R3-432AXSP06	155.5	244.6	186.1	209.8	-	156	244	186.2	209.5	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB400R3-525AXSP06	184.7	284.7	218.8	245.1	-	185.2	284.3	219.1	245	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB400R3-532AXSP06	174.1	270.6	207.3	232.7	-	174.7	270.1	207.3	232.6	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB400R3-625AXSP06	196.4	299.3	231.3	258.6	489.7	196.9	298.9	231.6	258.2	488.5	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB400R3-632AXSP06	187.7	289	222.5	249.1	477.7	188.1	288.4	222.4	248.9	475.4	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550B3-425AXSP04	167.5	268	203.3	229.7	455.6	169.4	269.2	204.7	230.7	455.9	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550B3-432AXSP06	164.9	259.5	197.4	222.7	-	165.5	259.5	198	223	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550B3-525AXSP06	192.9	298.1	229	256.7	-	194	298.4	229.6	257.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550B3-532AXSP06	183.1	285.4	218.1	245.1	-	184.2	285.6	219	245.6	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	456	12.4	(2) 4"	365	10.6	4"	548	17.4	(2) 4"
EAW-FD15S4ZB550B3-632AXSP06	-	-	-	-	-	197	302.2	233	260.5	499.4	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C3-425AXSP04	178.6	286.3	216.3	244.9	486.8	180.6	286.9	217.7	245.8	486.7	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550C2-432AXSP06	174.2	275	208.9	235.7	-	175.1	274.8	209.4	236	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550C2-525AXSP06	207.6	321.5	246.3	276.4	-	208.6	321.6	247.1	277.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C3-532AXSP06	195.5	304.9	233.1	262.2	-	196.4	305.2	233.3	262.4	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C3-625AXSP06	220.1	336.9	259.8	290.4	-	221.1	337.3	260.7	291.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C3-632AXSP06	210.7	325.4	249.8	280.2	-	211.6	325.3	250.5	280.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C3-425AXSP04	178.6	286.3	216.3	244.9	486.8	180.6	286.9	217.7	245.8	486.7	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550C3-432AXSP06	174.2	275	208.9	235.7	-	175.1	274.8	209.4	236	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550C3-525AXSP06	207.6	321.5	246.3	276.4	-	208.6	321.6	247.1	277.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C3-532AXSP06	195.5	304.9	233.1	262.2	-	196.4	305.2	233.3	262.4	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C3-625AXSP06	220.1	336.9	259.8	290.4	-	221.1	337.3	260.7	291.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C3-632AXSP06	210.7	325.4	249.8	280.2	-	211.6	325.3	250.5	280.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C4-425AXSP04	178.6	286.3	216.3	244.9	486.8	180.6	286.9	217.7	245.8	486.7	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550C4-432AXSP06	174.2	275	208.9	235.7	-	175.1	274.8	209.4	236	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550C4-525AXSP06	207.6	321.5	246.3	276.4	-	208.6	321.6	247.1	277.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C4-532AXSP06	195.5	304.9	233.1	262.2	-	196.4	305.2	233.3	262.4	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C4-625AXSP06	220.1	336.9	259.8	290.4	-	221.1	337.3	260.7	291.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C4-632AXSP06	210.7	325.4	249.8	280.2	-	211.6	325.3	250.5	280.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C4-425AXSP04	178.6	286.3	216.3	244.9	486.8	180.6	286.9	217.7	245.8	486.7	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550C4-432AXSP06	174.2	275	208.9	235.7	-	175.1	274.8	209.4	236	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550C4-525AXSP06	207.6	321.5	246.3	276.4	-	208.6	321.6	247.1	277.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C4-532AXSP06	195.5	304.9	233.1	262.2	-	196.4	305.2	233.3	262.4	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C4-625AXSP06	220.1	336.9	259.8	290.4	-	221.1	337.3	260.7	291.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C4-632AXSP06	210.7	325.4	249.8	280.2	-	211.6	325.3	250.5	280.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C8-425AXSP04	178.6	286.3	216.3	244.9	486.8	180.6	286.9	217.7	245.8	486.7	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550C8-432AXSP06	174.2	275	208.9	235.7	-	175.1	274.8	209.4	236	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550C8-525AXSP06	207.6	321.5	246.3	276.4	-	208.6	321.6	247.1	277.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C8-532AXSP06	195.5	304.9	233.1	262.2	-	196.4	305.2	233.3	262.4	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C8-625AXSP06	220.1	336.9	259.8	290.4	-	221.1	337.3	260.7	291.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C8-632AXSP06	210.7	325.4	249.8	280.2	-	211.6	325.3	250.5	280.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C9-425AXSP04	178.6	286.3	216.3	244.9	486.8	180.6	286.9	217.7	245.8	486.7	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550C9-432AXSP06	174.2	275	208.9	235.7	-	175.1	274.8	209.4	236	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550C9-525AXSP06	207.6	321.5	246.3	276.4	-	208.6	321.6	247.1	277.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C9-532AXSP06	195.5	304.9	233.1	262.2	-	196.4	305.2	233.3	262.4	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550C9-625AXSP06	220.1	336.9	259.8	290.4	-	221.1	337.3	260.7	291.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550C9-632AXSP06	210.7	325.4	249.8	280.2	-	211.6	325.3	250.5	280.4	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550K2-425AXSP04	171.1	274.1	207.4	234.4	465.7	172.8	274.8	208.3	235.3	465	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550K2-432AXSP06	167.3	263.6	200.4	226.1	-	168	263.3	200.8	226.2	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550K2-525AXSP06	199.3	308.5	236.7	265.5	-	200.1	308.3	236.9	265.7	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550K2-532AXSP06	187.6	292.3	223.5	251.3	-	188.2	292.1	223.8	251.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550K2-625AXSP06	212.2	324.4	250.4	279.8	-	213	324.4	250.7	280.1	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550K2-632AXSP06	202.8	312.5	240.2	269.3	-	203.5	312.1	240.4	269.3	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB550K3-425AXSP04	171.1	274.1	207.4	234.4	465.7	172.8	274.8	208.3	235.3	465	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB550K3-432AXSP06	167.3	263.6	200.4	226.1	-	168	263.3	200.8	226.2	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB550K3-525AXSP06	199.3	308.5	236.7	265.5	-	200.1	308.3	236.9	265.7	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB550K3-532AXSP06	187.6	292.3	223.5	251.3	-	188.2	292.1	223.8	251.5	-</									

EAW-FD15S4ZB750K2-625AXSP06	222.7	341.2	263.3	294.4	-	224	341.7	264.1	295.2	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K2-632AXSP06	212.8	329.3	252.7	283.5	-	214.1	329.3	253.5	283.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K3-425AXSP04	180.8	289.2	219	247.8	492.9	182.6	290.4	220.2	248.7	492.9	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K3-432AXSP04	167	269.8	203.4	230.4	462.2	168.8	270.7	204.7	231.5	461.5	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K3-525AXSP06	209.7	325	249.2	279.8	-	211.1	325.7	250.1	280.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K3-532AXSP06	197.7	308.5	235.8	264.8	-	198.6	308.8	236	265.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K3-625AXSP06	222.7	341.2	263.3	294.4	-	224	341.7	264.1	295.2	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K3-632AXSP06	212.8	329.3	252.7	283.5	-	214.1	329.3	253.5	283.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K4-425AXSP04	180.8	289.2	219	247.8	492.9	182.6	290.4	220.2	248.7	492.9	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K4-432AXSP04	167	269.8	203.4	230.4	462.2	168.8	270.7	204.7	231.5	461.5	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K4-525AXSP06	209.7	325	249.2	279.8	-	211.1	325.7	250.1	280.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K4-532AXSP06	197.7	308.5	235.8	264.8	-	198.6	308.8	236	265.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K4-625AXSP06	222.7	341.2	263.3	294.4	-	224	341.7	264.1	295.2	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K4-632AXSP06	212.8	329.3	252.7	283.5	-	214.1	329.3	253.5	283.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K5-425AXSP04	180.8	289.2	219	247.8	492.9	182.6	290.4	220.2	248.7	492.9	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K5-432AXSP04	167	269.8	203.4	230.4	462.2	168.8	270.7	204.7	231.5	461.5	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K5-525AXSP06	209.7	325	249.2	279.8	-	211.1	325.7	250.1	280.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K5-532AXSP06	197.7	308.5	235.8	264.8	-	198.6	308.8	236	265.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K5-625AXSP06	222.7	341.2	263.3	294.4	-	224	341.7	264.1	295.2	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K5-632AXSP06	212.8	329.3	252.7	283.5	-	214.1	329.3	253.5	283.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K8-425AXSP04	180.8	289.2	219	247.8	492.9	182.6	290.4	220.2	248.7	492.9	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K8-432AXSP04	167	269.8	203.4	230.4	462.2	168.8	270.7	204.7	231.5	461.5	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K8-525AXSP06	209.7	325	249.2	279.8	-	211.1	325.7	250.1	280.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K8-532AXSP06	197.7	308.5	235.8	264.8	-	198.6	308.8	236	265.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K8-625AXSP06	222.7	341.2	263.3	294.4	-	224	341.7	264.1	295.2	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K8-632AXSP06	212.8	329.3	252.7	283.5	-	214.1	329.3	253.5	283.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K9-425AXSP04	180.8	289.2	219	247.8	492.9	182.6	290.4	220.2	248.7	492.9	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K9-432AXSP04	167	269.8	203.4	230.4	462.2	168.8	270.7	204.7	231.5	461.5	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750K9-525AXSP06	209.7	325	249.2	279.8	-	211.1	325.7	250.1	280.3	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K9-532AXSP06	197.7	308.5	235.8	264.8	-	198.6	308.8	236	265.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750K9-625AXSP06	222.7	341.2	263.3	294.4	-	224	341.7	264.1	295.2	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750K9-632AXSP06	212.8	329.3	252.7	283.5	-	214.1	329.3	253.5	283.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750R3-425AXSP04	177	283.6	214.6	242.6	482.7	178.9	284.6	215.9	243.9	482.5	304	13.4	4"	244	11.7	3"	365	18.8	4"
EAW-FD15S4ZB750R3-432AXSP06	173.1	272.9	207.5	234.1	-	173.8	273	207.9	234.5	-	203	19.8	3"	162	13	3"	244	27.8	3"
EAW-FD15S4ZB750R3-525AXSP06	205.6	318.3	244.3	274.1	-	206.5	318.8	245	274.5	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750R3-532AXSP06	193.7	302.4	231	259.8	-	194.6	302.2	231.6	259.9	-	254	21.5	3"	203	14.1	3"	304	25.7	4"
EAW-FD15S4ZB750R3-625AXSP06	218.4	334.2	257.8	288.1	-	219.5	334.1	258.4	288.8	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZB750R3-632AXSP06	208.8	322.2	247.5	277.5	-	209.6	322.5	248.1	278.1	-	304	19	4"	244	15.4	3"	365	26.6	4"
EAW-FD15S4ZK370C2-425AXSP04	175.6	278.1	211.6	238.6	470.1	176.6	278.1	212	239	468.3	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK370C2-432AXSP06	170.7	267.3	204	229.5	-	171.1	266.9	203.8	229.1	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK370C2-525AXSP06	202.7	311.1	239.6	268.4	-	203.2	310.5	239.6	268.2	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C2-532AXSP06	191.3	296.2	227.2	254.9	-	191.9	295.6	227.1	254.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C2-625AXSP06	214.9	326.2	252.6	281.9	-	215.5	325.5	252.7	281.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C2-632AXSP06	206.3	315.8	243.8	272.4	-	206.7	315.1	243.6	272.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C4-425AXSP04	175.6	278.1	211.6	238.6	470.1	176.6	278.1	212	239	468.3	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK370C4-432AXSP06	170.7	267.3	204	229.5	-	171.1	266.9	203.8	229.1	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK370C4-525AXSP06	202.7	311.1	239.6	268.4	-	203.2	310.5	239.6	268.2	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C4-532AXSP06	191.3	296.2	227.2	254.9	-	191.9	295.6	227.1	254.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C4-625AXSP06	214.9	326.2	252.6	281.9	-	215.5	325.5	252.7	281.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C4-632AXSP06	206.3	315.8	243.8	272.4	-	206.7	315.1	243.6	272.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C5-425AXSP04	175.6	278.1	211.6	238.6	470.1	176.6	278.1	212	239	468.3	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK370C5-432AXSP06	170.7	267.3	204	229.5	-	171.1	266.9	203.8	229.1	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK370C5-525AXSP06	202.7	311.1	239.6	268.4	-	203.2	310.5	239.6	268.2	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C5-532AXSP06	191.3	296.2	227.2	254.9	-	191.9	295.6	227.1	254.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C5-625AXSP06	214.9	326.2	252.6	281.9	-	215.5	325.5	252.7	281.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C5-632AXSP06	206.3	315.8	243.8	272.4	-	206.7	315.1	243.6	272.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C8-425AXSP04	175.6	278.1	211.6	238.6	470.1	176.6	278.1	212	239	468.3	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK370C8-432AXSP06	170.7	267.3	204	229.5	-	171.1	266.9	203.8	229.1	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK370C8-525AXSP06	202.7	311.1	239.6	268.4	-	203.2	310.5	239.6	268.2	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C8-532AXSP06	191.3	296.2	227.2	254.9	-	191.9	295.6	227.1	254.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK370C8-625AXSP06	214.9	326.2	252.6	281.9	-	215.5	325.5	252.7	281.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370C8-632AXSP06	206.3	315.8	243.8	272.4	-	206.7	315.1	243.6	272.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK370K2-425AXSP04	169.9	269.1	204.7	230.7	454.1	170.7	268.7	205.2	230.7	451.8	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK370K2-432AXSP06	165.3	258.3	197.2	222	-	165.5	257.6	196.9	221.7	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK370K2-525AXSP06	197	301.9																	

EAW-FD15S4ZK400C9-532AXSP06	191.3	296.2	227.2	254.9	-	191.9	295.6	227.1	254.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400C9-625AXSP06	214.9	326.2	252.6	281.9	-	215.5	325.5	252.7	281.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400C9-632AXSP06	206.3	315.8	243.8	272.4	-	206.7	315.1	243.6	272.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400K3-425AXSP04	169.9	269.1	204.7	230.7	454.1	170.7	268.7	205.2	230.7	451.8	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK400K3-432AXSP06	165.3	258.3	197.2	222	-	165.5	257.6	196.9	221.7	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK400K3-525AXSP06	197	301.9	232.8	260.2	-	196.9	300.9	232.4	259.7	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400K3-532AXSP06	185.4	287	220.1	247.2	-	185.6	285.9	220	246.6	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400K3-625AXSP06	209.9	317.9	246.7	274.9	-	209.9	316.8	246.1	274.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400K3-632AXSP06	200.4	306.8	236.7	264.8	505	200.5	305.7	236.2	264.2	502.4	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400K9-425AXSP04	169.9	269.1	204.7	230.7	454.1	170.7	268.7	205.2	230.7	451.8	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK400K9-432AXSP06	165.3	258.3	197.2	222	-	165.5	257.6	196.9	221.7	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK400K9-525AXSP06	197	301.9	232.8	260.2	-	196.9	300.9	232.4	259.7	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400K9-532AXSP06	185.4	287	220.1	247.2	-	185.6	285.9	220	246.6	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400K9-625AXSP06	209.9	317.9	246.7	274.9	-	209.9	316.8	246.1	274.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400K9-632AXSP06	200.4	306.8	236.7	264.8	505	200.5	305.7	236.2	264.2	502.4	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400R3-425AXSP04	172	273	207.5	234	460.3	173.2	272.8	207.8	234.2	458.9	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK400R3-432AXSP06	167.5	262.3	199.9	224.9	-	167.6	261.2	199.9	224.7	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD15S4ZK400R3-525AXSP06	199.1	305.8	235.4	263.5	-	199.4	304.9	235.4	263.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400R3-532AXSP06	187.8	290.9	222.9	250.1	-	188.2	290.1	222.7	249.7	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK400R3-625AXSP06	212.3	322	249.5	278.4	-	212.4	321.1	249.1	277.5	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK400R3-632AXSP06	202.8	310.7	239.6	268.1	-	203	309.7	239.2	267.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550B3-425AXSP04	183.6	291	220.9	249.3	492.1	185.1	291.7	221.9	250.3	491.3	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550B3-432AXSP04	170.2	272.4	206.2	233.2	463.6	171.7	272.6	207	233.7	462.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550B3-525AXSP06	210.9	324.2	249.4	279.5	-	211.6	323.9	249.9	279.6	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550B3-625AXSP06	199.5	309.6	237	266.2	-	200.2	309.2	237.5	266.2	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550B3-632AXSP06	222.5	337.7	261.7	292.1	-	223.3	337.7	262	292.5	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550B3-632AXSP06	214.1	328.4	253.1	283.4	-	214.9	328.6	253.6	283.5	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C2-425AXSP04	195	309.1	234.7	264.8	-	196.4	309.6	235.6	265.7	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C2-432AXSP04	179.7	287.6	217.4	245.9	489.9	181	288	218.3	246.5	488.5	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C2-525AXSP04	214.4	337.4	257.2	289.4	564.7	215.9	337.9	258.5	290.2	564.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD15S4ZK550C2-532AXSP06	212.1	329.3	252.3	283.1	-	212.6	328.9	252.4	283.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550C2-625AXSP06	240.2	366.1	283.1	316.3	-	240.9	365.8	283.1	316.3	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C2-632AXSP06	229.2	352.6	271.2	303.9	-	229.7	352.4	271.4	303.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C3-425AXSP04	195	309.1	234.7	264.8	-	196.4	309.6	235.6	265.7	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C3-432AXSP04	179.7	287.6	217.4	245.9	489.9	181	288	218.3	246.5	488.5	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C3-525AXSP04	214.4	337.4	257.2	289.4	564.7	215.9	337.9	258.5	290.2	564.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD15S4ZK550C3-532AXSP06	212.1	329.3	252.3	283.1	-	212.6	328.9	252.4	283.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550C3-625AXSP06	240.2	366.1	283.1	316.3	-	240.9	365.8	283.1	316.3	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C3-632AXSP06	229.2	352.6	271.2	303.9	-	229.7	352.4	271.4	303.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C4-425AXSP04	195	309.1	234.7	264.8	-	196.4	309.6	235.6	265.7	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C4-432AXSP04	179.7	287.6	217.4	245.9	489.9	181	288	218.3	246.5	488.5	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C4-525AXSP04	214.4	337.4	257.2	289.4	564.7	215.9	337.9	258.5	290.2	564.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD15S4ZK550C4-532AXSP06	212.1	329.3	252.3	283.1	-	212.6	328.9	252.4	283.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550C4-625AXSP06	240.2	366.1	283.1	316.3	-	240.9	365.8	283.1	316.3	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C4-632AXSP06	229.2	352.6	271.2	303.9	-	229.7	352.4	271.4	303.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C5-425AXSP04	195	309.1	234.7	264.8	-	196.4	309.6	235.6	265.7	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C5-432AXSP04	179.7	287.6	217.4	245.9	489.9	181	288	218.3	246.5	488.5	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C5-525AXSP04	214.4	337.4	257.2	289.4	564.7	215.9	337.9	258.5	290.2	564.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD15S4ZK550C5-532AXSP06	212.1	329.3	252.3	283.1	-	212.6	328.9	252.4	283.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550C5-625AXSP06	240.2	366.1	283.1	316.3	-	240.9	365.8	283.1	316.3	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C5-632AXSP06	229.2	352.6	271.2	303.9	-	229.7	352.4	271.4	303.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C8-425AXSP04	195	309.1	234.7	264.8	-	196.4	309.6	235.6	265.7	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C8-432AXSP04	179.7	287.6	217.4	245.9	489.9	181	288	218.3	246.5	488.5	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C8-525AXSP04	214.4	337.4	257.2	289.4	564.7	215.9	337.9	258.5	290.2	564.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD15S4ZK550C8-532AXSP06	212.1	329.3	252.3	283.1	-	212.6	328.9	252.4	283.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550C8-625AXSP06	240.2	366.1	283.1	316.3	-	240.9	365.8	283.1	316.3	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C8-632AXSP06	229.2	352.6	271.2	303.9	-	229.7	352.4	271.4	303.6	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD15S4ZK550C9-425AXSP04	195	309.1	234.7	264.8	-	196.4	309.6	235.6	265.7	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C9-432AXSP04	179.7	287.6	217.4	245.9	489.9	181	288	218.3	246.5	488.5	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550C9-525AXSP04	214.4	337.4	257.2	289.4	564.7	215.9	337.9	258.5	290.2	564.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD15S4ZK550C9-532AXSP06	212.1	329.3	252.3	283.1	-	212.6	328.9	252.4	283.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD15S4ZK550K2-425AXSP04	186.3	295.7	224.3	253.2	500.4	187.5	295.9	225.3	253.8	498.8	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550K2-432AXSP04	172	275.2	208.4	235.5	468.6	173.2	275.5	208.9	235.9	467	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD15S4ZK550K2-525AXSP06	215.6	332	255.5	286	-	216.2	331.4	255.5	285.9	-	254	23.2	3"	203	15.3</				

EAW-FD1554ZK550R3-525AXSP06	220	339	260.8	292	-	220.4	338.6	260.8	292	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK550R3-532AXSP06	206.8	321.1	245.9	276.3	-	207.3	320.7	246	276.3	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK550R3-625AXSP06	235	357.4	276.4	308.8	-	235.2	356.8	276.4	308.7	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK550R3-632AXSP06	223.6	344.1	264.9	296.3	-	224.2	343	264.8	296.2	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750C4-425AXSP06	212.6	332.5	253.7	285.5	-	213.5	332.9	254.5	285.8	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD1554ZK750C4-432AXSP06	196.9	309.7	235.8	265.8	-	197.7	309.6	236.2	265.8	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD1554ZK750C4-525AXSP06	234.4	361.9	278.1	311.6	-	235.6	362.5	278.6	312.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750C4-532AXSP06	220.9	343.7	262.9	295.1	-	221.5	343.5	263.1	295.4	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750C4-632AXSP06	237.9	366.7	281.6	315.7	-	238.9	366.6	282.3	316	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750C5-425AXSP06	212.6	332.5	253.7	285.5	-	213.5	332.9	254.5	285.8	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD1554ZK750C5-432AXSP06	196.9	309.7	235.8	265.8	-	197.7	309.6	236.2	265.8	-	203	21.5	3"	162	14.2	3"	244	30.2	3"
EAW-FD1554ZK750C5-525AXSP06	234.4	361.9	278.1	311.6	-	235.6	362.5	278.6	312.1	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750C5-532AXSP06	220.9	343.7	262.9	295.1	-	221.5	343.5	263.1	295.4	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750C5-632AXSP06	237.9	366.7	281.6	315.7	-	238.9	366.6	282.3	316	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K2-425AXSP04	197.7	313.8	237.9	268.8	-	199.3	314.1	238.9	269.4	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K2-432AXSP04	182.6	292.2	220.9	249.9	498.7	184	292.6	221.8	250.5	497.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K2-525AXSP04	217	341.2	260.4	293	572.1	218.5	341.8	261.7	293.9	571.2	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750K3-525AXSP06	214.5	333.8	255.1	286.9	-	215.2	333.2	255.6	286.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750K2-625AXSP06	243.2	370.9	286.2	319.9	-	244	370.6	286.8	320.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K2-632AXSP06	232	357.1	274.5	307.7	-	232.5	356.3	274.7	307.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K3-425AXSP04	197.7	313.8	237.9	268.8	-	199.3	314.1	238.9	269.4	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K3-432AXSP04	182.6	292.2	220.9	249.9	498.7	184	292.6	221.8	250.5	497.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K3-525AXSP06	217	341.2	260.4	293	572.1	218.5	341.8	261.7	293.9	571.2	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750K3-532AXSP06	214.5	333.8	255.1	286.9	-	215.2	333.2	255.6	286.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750K3-625AXSP06	243.2	370.9	286.2	319.9	-	244	370.6	286.8	320.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K3-632AXSP06	232	357.1	274.5	307.7	-	232.5	356.3	274.7	307.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K4-425AXSP04	197.7	313.8	237.9	268.8	-	199.3	314.1	238.9	269.4	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K4-432AXSP04	182.6	292.2	220.9	249.9	498.7	184	292.6	221.8	250.5	497.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K4-525AXSP04	217	341.2	260.4	293	572.1	218.5	341.8	261.7	293.9	571.2	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750K4-532AXSP06	214.5	333.8	255.1	286.9	-	215.2	333.2	255.6	286.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750K4-625AXSP06	243.2	370.9	286.2	319.9	-	244	370.6	286.8	320.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K4-632AXSP06	232	357.1	274.5	307.7	-	232.5	356.3	274.7	307.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K5-425AXSP04	197.7	313.8	237.9	268.8	-	199.3	314.1	238.9	269.4	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K5-432AXSP04	182.6	292.2	220.9	249.9	498.7	184	292.6	221.8	250.5	497.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K5-525AXSP06	217	341.2	260.4	293	572.1	218.5	341.8	261.7	293.9	571.2	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750K5-532AXSP06	214.5	333.8	255.1	286.9	-	215.2	333.2	255.6	286.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750K5-625AXSP06	243.2	370.9	286.2	319.9	-	244	370.6	286.8	320.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K5-632AXSP06	232	357.1	274.5	307.7	-	232.5	356.3	274.7	307.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K8-425AXSP04	197.7	313.8	237.9	268.8	-	199.3	314.1	238.9	269.4	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K8-432AXSP04	182.6	292.2	220.9	249.9	498.7	184	292.6	221.8	250.5	497.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K8-525AXSP04	217	341.2	260.4	293	572.1	218.5	341.8	261.7	293.9	571.2	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750K8-532AXSP06	214.5	333.8	255.1	286.9	-	215.2	333.2	255.6	286.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750K8-625AXSP06	243.2	370.9	286.2	319.9	-	244	370.6	286.8	320.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K8-632AXSP06	232	357.1	274.5	307.7	-	232.5	356.3	274.7	307.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K9-425AXSP04	197.7	313.8	237.9	268.8	-	199.3	314.1	238.9	269.4	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K9-432AXSP04	182.6	292.2	220.9	249.9	498.7	184	292.6	221.8	250.5	497.7	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750K9-525AXSP06	217	341.2	260.4	293	572.1	218.5	341.8	261.7	293.9	571.2	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750K9-532AXSP06	214.5	333.8	255.1	286.9	-	215.2	333.2	255.6	286.8	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750K9-625AXSP06	243.2	370.9	286.2	319.9	-	244	370.6	286.8	320.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750K9-632AXSP06	232	357.1	274.5	307.7	-	232.5	356.3	274.7	307.4	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750R3-425AXSP04	193.5	306.8	233.1	262.9	-	195.1	307.6	233.8	264	-	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750R3-432AXSP04	179	286.2	216.7	245.1	487.7	180.5	287.1	217.4	245.7	486.8	304	14.5	4"	244	12.5	3"	365	20.4	4"
EAW-FD1554ZK750R3-525AXSP04	212.3	334	255.1	287	559.5	214.1	334.4	255.9	287.8	558.5	378	15.7	4"	302	10.3	4"	453	18.4	(2) 4"
EAW-FD1554ZK750R3-532AXSP06	210.4	326.9	250.2	281.2	-	211	326.3	250.5	281	-	254	23.2	3"	203	15.3	3"	304	28.1	4"
EAW-FD1554ZK750R3-625AXSP06	237.8	362.3	280.2	313	-	238.7	362.3	280.6	313	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1554ZK750R3-632AXSP06	227	349.1	269	300.9	-	227.8	348.8	269.1	301	-	304	20.7	4"	244	16.6	3"	365	29	4"
EAW-FD1555PB370C2-425AXSP04	191.3	301.3	229	258.6	-	192.6	302.1	230.1	259.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD1555PB370C2-432AXSP04	178.2	282.7	214.3	241.9	-	179.4	282.8	215	242.6	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD1555PB370C2-525AXSP04	208.6	325.1	248.6	279.4	541.9	210.3	326.1	250.2	280.6	541.9	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD1555PB370C2-532AXSP04	197.6	310.9	237.3	267.2	522.3	199	311.5	238.2	267.7	522.3	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD1555PB370C2-625AXSP06	228	345.5	267.7	298.9	-	229.3	346.3	268.6	299.4	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD1555PB370C2-632AXSP06	220.2	337.2	260.3	291	-	221.3	337.5	260.8	291.6	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD1555PB370C4-425AXSP04	191.3	301.3	229	258.6	-	192.6	302.1	230.1	259.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD1555PB370C4-432AXSP04	178.2	282.7	214.3	241.9	-	179.4	282.8	215	242.6	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD1555PB370C4-525AXSP04	208.6	325.1	248																

EAW-FD155SPB370K8-532AXSP04	193.8	305	232.6	261.9	512	195.1	304.9	233.3	262.1	510.7	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB370K8-625AXSP06	227.5	344.8	267.2	298.3	-	227.9	344.1	267.3	298	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB370K8-632AXSP06	217.7	333.2	257.3	287.6	-	218.1	332.9	257	287.3	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400B3-425AXSP04	184.2	289.9	220.8	248.6	-	185.9	290.9	221.9	249.8	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400B3-432AXSP04	172.2	273.1	207.2	233.9	-	173.5	273.9	208.2	234.7	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400B3-525AXSP04	-	-	-	-	-	-	-	-	-	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400B3-532AXSP04	190.4	299.3	228.4	257.1	502	191.9	300.1	229.4	257.7	501.6	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB400B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB400C3-425AXSP04	191.3	301.3	229	258.6	-	192.6	302.1	230.1	259.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400C3-432AXSP04	178.2	282.7	214.3	241.9	-	179.4	282.8	215	242.6	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400C3-525AXSP04	208.6	325.1	248.6	279.4	541.9	210.3	326.1	250.2	280.6	541.9	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400C3-532AXSP04	197.6	310.9	237.3	267.2	522.3	199	311.5	238.2	267.7	522.3	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400C3-625AXSP06	228	345.5	267.7	298.9	-	229.3	346.3	268.6	299.4	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400C3-632AXSP06	220.2	337.2	260.3	291	-	221.3	337.5	260.8	291.6	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400C9-425AXSP04	191.3	301.3	229	258.6	-	192.6	302.1	230.1	259.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400C9-432AXSP04	178.2	282.7	214.3	241.9	-	179.4	282.8	215	242.6	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400C9-525AXSP04	208.6	325.1	248.6	279.4	541.9	210.3	326.1	250.2	280.6	541.9	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400C9-532AXSP04	197.6	310.9	237.3	267.2	522.3	199	311.5	238.2	267.7	522.3	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400C9-625AXSP06	228	345.5	267.7	298.9	-	229.3	346.3	268.6	299.4	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400C9-632AXSP06	220.2	337.2	260.3	291	-	221.3	337.5	260.8	291.6	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400K3-425AXSP04	186.9	294.5	224.1	252.4	-	188	294.5	224.9	253.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400K3-432AXSP04	173.5	275.3	208.8	235.8	-	174.6	275.5	209.4	236.3	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400K3-525AXSP04	205.8	320.6	245.7	276	534.2	207.1	321	246.4	276.3	533.2	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400K3-532AXSP04	193.8	305	232.6	261.9	512	195.1	304.9	233.3	262.1	510.7	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400K3-625AXSP06	227.5	344.8	267.2	298.3	-	227.9	344.1	267.3	298	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400K3-632AXSP06	217.7	333.2	257.3	287.6	-	218.1	332.9	257	287.3	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400K9-425AXSP04	186.9	294.5	224.1	252.4	-	188	294.5	224.9	253.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400K9-432AXSP04	173.5	275.3	208.8	235.8	-	174.6	275.5	209.4	236.3	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400K9-525AXSP04	205.8	320.6	245.7	276	534.2	207.1	321	246.4	276.3	533.2	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400K9-532AXSP04	193.8	305	232.6	261.9	512	195.1	304.9	233.3	262.1	510.7	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400K9-625AXSP06	227.5	344.8	267.2	298.3	-	227.9	344.1	267.3	298	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400K9-632AXSP06	217.7	333.2	257.3	287.6	-	218.1	332.9	257	287.3	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400R3-425AXSP04	189.1	297.6	226.3	255.5	-	190.3	297.8	227.3	256	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400R3-432AXSP04	175.5	278.3	211.2	238.3	-	176.7	278.6	211.8	238.9	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB400R3-525AXSP04	207.9	324	247.8	278.4	539.9	209.3	324	248.6	279.3	538.4	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400R3-532AXSP04	195.9	308.1	234.8	264.4	517.4	197	308	235.6	264.8	516.3	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB400R3-625AXSP06	229.6	348.1	269.6	300.6	-	230.1	347.5	269.5	300.4	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB400R3-632AXSP06	219.8	336.5	259.4	290.5	-	220.3	335.9	259.6	290.2	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB50B3-425AXSP04	197.1	311	236.4	266.6	-	198.9	312	238.1	267.8	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB50B3-432AXSP04	184.2	292.5	221.7	250.4	-	185.8	293.3	223	251.6	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB50B3-525AXSP02	-	-	-	-	-	-	-	-	-	-	676	9.5	(2) 4"	541	6.3	(2) 4"	812	13.4	(2) 4"
EAW-FD155SPB50B3-532AXSP04	-	-	-	-	-	205.5	321.6	245.6	276.1	539.1	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB50B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	10.7	(2) 4"	649	7	(2) 4"	974	12	(3) 4"
EAW-FD155SPB50B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550C2-425AXSP04	210.9	333.8	253.2	286	-	212.7	334.6	254.8	287.1	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C2-432AXSP04	195.6	311.4	235.6	266.2	-	197.1	312	236.8	267.4	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C2-525AXSP04	231.7	361.5	276.1	310.8	-	233.4	362.9	277.7	311.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C2-532AXSP04	218.6	343.7	262	295.1	-	220.1	344.8	263.3	296	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C2-632AXSP04	-	-	-	-	-	236	367	281.5	315.9	610.7	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550C3-425AXSP04	210.9	333.8	253.2	286	-	212.7	334.6	254.8	287.1	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C3-432AXSP04	195.6	311.4	235.6	266.2	-	197.1	312	236.8	267.4	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C3-525AXSP04	231.7	361.5	276.1	310.8	-	233.4	362.9	277.7	311.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C3-532AXSP04	218.6	343.7	262	295.1	-	220.1	344.8	263.3	296	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	10.7	(2) 4"	649	7	(2) 4"	974	12	(3) 4"
EAW-FD155SPB550C3-632AXSP04	-	-	-	-	-	236	367	281.5	315.9	610.7	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550C4-425AXSP04	210.9	333.8	253.2	286	-	212.7	334.6	254.8	287.1	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C4-432AXSP04	195.6	311.4	235.6	266.2	-	197.1	312	236.8	267.4	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C4-525AXSP04	231.7	361.5	276.1	310.8	-	233.4	362.9	277.7	311.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C4-532AXSP04	218.6	343.7	262	295.1	-	220.1	344.8	263.3	296	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C4-632AXSP04	-	-	-	-	-	236	367	281.5	315.9	610.7	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550C5-425AXSP04	210.9	333.8	253.2	286	-	212.7	334.6	254.8	287.1	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C5-432AXSP04	195.6	311.4	235.6	266.2	-	197.1	312	236.8	267.4	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550C5-525AXSP04	231.7	361.5	276.1	310.8	-	233.4	362.9	277.7	311.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C5-532AXSP04	218.6	343.7	262	295.1	-	220.1	344.8	263.3	296	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550C5-632AXSP04	-	-	-	-	-	236	367	281.5	315.9	610.7	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550C8-425AXSP04	210.9	333.8	253.2	286	-	212.7	334.6	254.8	287.										

EAW-FD155SPB550K8-425AXSP04	203.3	321	243.8	274.9	-	204.6	321.6	244.6	275.8	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550K8-432AXSP04	188.2	299.2	226.6	256.1	-	189.6	299.8	227.4	256.7	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550K8-525AXSP04	224.2	349.6	267	300.3	-	225.6	350.1	268.3	301.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550K8-532AXSP04	210.8	331.8	252.5	284.7	558.1	212.2	332.2	253.7	285.4	557.6	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550K8-625AXSP04	237.5	367	282.6	316.6	607.3	239.1	367.9	283.3	317.3	606.4	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550K8-632AXSP06	236.3	362.5	279.1	312.4	-	236.8	362.3	279.3	312.5	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB550K9-425AXSP04	203.3	321	243.8	274.9	-	204.6	321.6	244.6	275.8	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550K9-432AXSP04	188.2	299.2	226.6	256.1	-	189.6	299.8	227.4	256.7	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550K9-525AXSP04	224.2	349.6	267	300.3	-	225.6	350.1	268.3	301.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550K9-532AXSP04	210.8	331.8	252.5	284.7	558.1	212.2	332.2	253.7	285.4	557.6	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550K9-625AXSP04	237.5	367	282.6	316.6	607.3	239.1	367.9	283.3	317.3	606.4	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550K9-632AXSP06	236.3	362.5	279.1	312.4	-	236.8	362.3	279.3	312.5	-	270	22.3	4"	216	17	3"	325	31.3	4"
EAW-FD155SPB550R3-425AXSP04	206.7	326.9	248	279.8	-	208.2	327	248.9	280.9	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550R3-432AXSP04	191.5	304.5	230.6	260.5	-	192.9	305.1	231.6	261.4	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB550R3-525AXSP04	227.7	355.5	271.8	305.3	-	229.3	356.3	272.8	306.3	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550R3-532AXSP04	214	337.4	257	289.3	-	215.8	338.2	258	290.4	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB550R3-625AXSP04	241.6	373.6	287.1	322.1	617.7	243.3	374.2	288.4	323	617.7	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB550R3-632AXSP04	230.5	359.8	275.3	309.5	600.4	232	360.4	276.6	310.3	599.4	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K2-425AXSP04	213.2	337	256	289.3	-	215	338.6	257.7	290.5	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K2-432AXSP04	197.8	314.8	238.2	269.3	-	199.3	315.4	239.2	270.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K2-525AXSP04	234.3	366.5	279.8	314.5	-	236.3	367.7	281.2	315.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K2-532AXSP04	220.7	347.5	264.7	298.3	-	222.5	348.8	266.2	299.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K2-625AXSP04	248.3	384.5	295.2	331.3	636.1	250.4	385.5	296.9	332.6	636.1	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K2-632AXSP04	236.8	370.3	283.4	318.2	618.5	239	371.3	284.6	319.5	618.3	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K3-425AXSP04	213.2	337	256	289.3	-	215	338.6	257.7	290.5	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K3-432AXSP04	197.8	314.8	238.2	269.3	-	199.3	315.4	239.2	270.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K3-525AXSP04	234.3	366.5	279.8	314.5	-	236.3	367.7	281.2	315.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K3-532AXSP04	220.7	347.5	264.7	298.3	-	222.5	348.8	266.2	299.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K3-625AXSP04	248.3	384.5	295.2	331.3	636.1	250.4	385.5	296.9	332.6	636.1	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K3-632AXSP04	236.8	370.3	283.4	318.2	618.5	239	371.3	284.6	319.5	618.3	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K4-425AXSP04	213.2	337	256	289.3	-	215	338.6	257.7	290.5	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K4-432AXSP04	197.8	314.8	238.2	269.3	-	199.3	315.4	239.2	270.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K4-525AXSP04	234.3	366.5	279.8	314.5	-	236.3	367.7	281.2	315.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K4-532AXSP04	220.7	347.5	264.7	298.3	-	222.5	348.8	266.2	299.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K4-625AXSP04	248.3	384.5	295.2	331.3	636.1	250.4	385.5	296.9	332.6	636.1	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K4-632AXSP04	236.8	370.3	283.4	318.2	618.5	239	371.3	284.6	319.5	618.3	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K5-425AXSP04	213.2	337	256	289.3	-	215	338.6	257.7	290.5	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K5-432AXSP04	197.8	314.8	238.2	269.3	-	199.3	315.4	239.2	270.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K5-525AXSP04	234.3	366.5	279.8	314.5	-	236.3	367.7	281.2	315.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K5-532AXSP04	220.7	347.5	264.7	298.3	-	222.5	348.8	266.2	299.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K5-625AXSP04	248.3	384.5	295.2	331.3	636.1	250.4	385.5	296.9	332.6	636.1	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K5-632AXSP04	236.8	370.3	283.4	318.2	618.5	239	371.3	284.6	319.5	618.3	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K8-425AXSP04	213.2	337	256	289.3	-	215	338.6	257.7	290.5	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K8-432AXSP04	197.8	314.8	238.2	269.3	-	199.3	315.4	239.2	270.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K8-525AXSP04	234.3	366.5	279.8	314.5	-	236.3	367.7	281.2	315.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K8-532AXSP04	220.7	347.5	264.7	298.3	-	222.5	348.8	266.2	299.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K8-625AXSP04	248.3	384.5	295.2	331.3	636.1	250.4	385.5	296.9	332.6	636.1	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K8-632AXSP04	236.8	370.3	283.4	318.2	618.5	239	371.3	284.6	319.5	618.3	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K9-425AXSP04	213.2	337	256	289.3	-	215	338.6	257.7	290.5	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K9-432AXSP04	197.8	314.8	238.2	269.3	-	199.3	315.4	239.2	270.2	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750K9-525AXSP04	234.3	366.5	279.8	314.5	-	236.3	367.7	281.2	315.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K9-625AXSP04	220.7	347.5	264.7	298.3	-	222.5	348.8	266.2	299.2	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750K9-632AXSP04	248.3	384.5	295.2	331.3	636.1	250.4	385.5	296.9	332.6	636.1	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750K9-632AXSP04	236.8	370.3	283.4	318.2	618.5	239	371.3	284.6	319.5	618.3	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750R3-425AXSP04	209.2	330.6	251.1	283.4	-	210.9	331.9	252.4	284.4	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750R3-432AXSP04	194	308.7	233.8	264.2	-	195.5	309.5	234.7	265.1	-	270	15.4	4"	216	12.5	3"	325	21.7	4"
EAW-FD155SPB750R3-525AXSP04	229.7	358.9	274.2	308.6	-	231.6	359.9	275.5	309.9	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750R3-532AXSP04	216.6	341.1	259.7	292.4	-	218.2	342.2	261	293.8	-	338	16.4	4"	270	10.8	4"	406	23.1	4"
EAW-FD155SPB750R3-625AXSP04	243.4	376.6	289.3	324.6	622.7	245.5	377.6	290.9	325.9	622.7	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SPB750R3-632AXSP04	232.3	363.5	278	312.6	606.7	234.4	364.3	279.1	313.7	606.2	406	17.6	4"	325	11.6	4"	487	20.6	(2) 4"
EAW-FD155SZB370C2-425AXSP04	208.1	327.4	248.8	280.7	-	209.3	327.5	249.9	281.2	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB370C2-432AXSP04	193.2	306.2	232.4	262.3	-	194.2	306.2	232.8	262.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB370C2-525AXSP04	227.1	353.5	270.5	303.9	588.8	228.3	353.8	271.6	304.5	587.5	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB370C2-532AXSP04	214.3	337.3	257.3	289.6	566.1	215.4	337.2	257.7	290	564.9	378	17.1							

EAW-FD155SZB370K5-632AXSP06	236.2	360.4	278.2	311.3	-	236.2	359.4	277.9	310.4	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB370K8-425AXSP04	202.1	311.5	242.1	272.5	-	203.4	317.6	242.7	273	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB370K8-432AXSP04	187.2	296.7	225.5	254.4	502.6	188.2	296.8	225.9	254.4	501.6	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB370K8-525AXSP04	221.7	345.3	264.5	297	574.8	222.7	345.2	264.8	297.3	572.8	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB370K8-532AXSP06	218.7	337.4	259.3	290.9	-	219	336.7	259.1	290.2	-	254	25.3	3"	203	16.7	3"	304	31.1	4"
EAW-FD155SZB370K8-625AXSP06	246.7	373.5	289.7	322.8	-	247.2	372.3	289.5	322.6	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB370K8-632AXSP06	236.2	360.4	278.2	311.3	-	236.2	359.4	277.9	310.4	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400B3-425AXSP04	201	315.6	240.3	270.9	-	202.3	315.9	241.4	271.5	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400B3-432AXSP04	187	296.5	225	254	502.2	188.1	296.7	225.8	254.2	501.4	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400B3-525AXSP04	217.9	339.1	259.9	291.8	564.1	219.6	340.1	261.1	293	564	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400B3-532AXSP06	216.7	334.7	256.9	288.1	-	217.1	334.3	256.9	288.2	-	254	25.3	3"	203	16.7	3"	304	31.1	4"
EAW-FD155ZB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155ZB400B3-632AXSP06	231.8	353.9	273.4	305.4	-	232.5	353.6	273.5	305.5	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400C3-425AXSP04	208.1	327.4	248.8	280.7	-	209.3	327.5	249.9	281.2	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400C3-432AXSP04	193.2	306.2	232.4	262.3	-	194.2	306.2	232.8	262.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400C3-525AXSP04	227.1	353.5	270.5	303.9	588.8	228.3	353.8	271.6	304.5	587.5	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400C3-532AXSP04	214.3	337.3	257.3	289.6	566.1	215.4	337.2	257.7	290	564.9	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400C3-625AXSP06	250.2	379	293.8	327.9	-	251.2	379	294.6	328.3	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400C3-632AXSP06	241.2	368.9	284.6	318.1	-	241.8	368.3	284.5	318	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400C3-632AXSP06	208.1	327.4	248.8	280.7	-	209.3	327.5	249.9	281.2	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400C9-432AXSP04	193.2	306.2	232.4	262.3	-	194.2	306.2	232.8	262.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400C9-525AXSP04	227.1	353.5	270.5	303.9	588.8	228.3	353.8	271.6	304.5	587.5	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400C9-632AXSP04	214.3	337.3	257.3	289.6	566.1	215.4	337.2	257.7	290	564.9	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400C9-625AXSP06	250.2	379	293.8	327.9	-	251.2	379	294.6	328.3	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400C9-632AXSP06	241.2	368.9	284.6	318.1	-	241.8	368.3	284.5	318	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400K3-425AXSP04	202.1	317.5	242.1	272.5	-	203.4	317.6	242.7	273	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400K3-432AXSP04	187.2	296.7	225.5	254.4	502.6	188.2	296.8	225.9	254.4	501.6	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400K3-525AXSP04	221.7	345.3	264.5	297	574.8	222.7	345.2	264.8	297.3	572.8	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400K3-532AXSP06	218.7	337.4	259.3	290.9	-	219	336.7	259.1	290.2	-	254	25.3	3"	203	16.7	3"	304	31.1	4"
EAW-FD155ZB400K3-625AXSP06	246.7	373.5	289.7	322.8	-	247.2	372.3	289.5	322.6	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400K3-632AXSP06	236.2	360.4	278.2	311.3	-	236.2	359.4	277.9	310.4	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400K9-425AXSP04	202.1	317.5	242.1	272.5	-	203.4	317.6	242.7	273	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400K9-432AXSP04	187.2	296.7	225.5	254.4	502.6	188.2	296.8	225.9	254.4	501.6	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400K9-525AXSP04	221.7	345.3	264.5	297	574.8	222.7	345.2	264.8	297.3	572.8	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400K9-625AXSP06	218.7	337.4	259.3	290.9	-	219	336.7	259.1	290.2	-	254	25.3	3"	203	16.7	3"	304	31.1	4"
EAW-FD155ZB400K9-632AXSP06	246.7	373.5	289.7	322.8	-	247.2	372.3	289.5	322.6	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400K9-632AXSP06	236.2	360.4	278.2	311.3	-	236.2	359.4	277.9	310.4	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400R3-425AXSP04	204.5	321.5	245	275.8	-	205.5	321.7	245.2	276.4	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400R3-432AXSP04	189.7	300.6	228.1	257.7	-	190.7	300.4	228.7	257.8	508	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB400R3-525AXSP04	224.1	349.2	267.4	300.3	581.5	225.5	349.2	268.3	300.7	579.7	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB400R3-532AXSP06	221.2	341.4	262.3	294.3	-	221.2	340.8	261.8	293.7	-	254	25.3	3"	203	16.7	3"	304	31.1	4"
EAW-FD155ZB400R3-625AXSP06	249.4	377.6	292.8	326.3	-	249.6	376.5	292.3	325.8	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB400R3-632AXSP06	238.7	364.3	281.6	314.7	-	238.8	363.5	280.9	313.9	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB550B3-425AXSP04	216	340.3	258.6	292	-	217.5	341.2	259.8	292.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550B3-432AXSP04	201.3	319.3	242	273.2	-	202.6	319.4	242.8	274	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550B3-525AXSP04	234.7	365.4	279.7	314.4	609.4	236.5	366.5	281	315.7	609.3	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550B3-532AXSP04	222.1	349.8	266.3	300	587.9	223.9	350.7	268	301.2	587.4	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155ZB550B3-632AXSP06	-	-	-	-	-	249.7	381	294.4	329.1	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155ZB550C2-425AXSP04	229.8	363.2	276	310.9	-	231.4	363.8	277.1	312	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550C2-432AXSP04	212.8	338	256	289.3	-	214.2	338.8	257	290	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550C2-525AXSP04	252.4	394	301.2	338.3	-	254.1	394.8	302.3	339.5	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550C2-532AXSP04	237.3	373.4	284.4	320.8	629.5	239	373.9	285.3	321.1	628	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550C2-625AXSP04	268.4	414.9	319	357.8	686.6	270.7	415.9	320.7	359.1	686.5	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155ZB550C2-632AXSP04	256.4	400.7	306.7	344.7	668.3	258.4	401.3	308.1	345.7	667.2	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155ZB550C3-425AXSP04	229.8	363.2	276	310.9	-	231.4	363.8	277.1	312	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550C3-525AXSP04	212.8	338	256	289.3	-	214.2	338.8	257	290	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550C3-532AXSP04	252.4	394	301.2	338.3	-	254.1	394.8	302.3	339.5	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550C3-632AXSP04	237.3	373.4	284.4	320.8	629.5	239	373.9	285.3	321.1	628	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550C3-625AXSP04	268.4	414.9	319	357.8	686.6	270.7	415.9	320.7	359.1	686.5	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155ZB550C3-632AXSP04	256.4	400.7	306.7	344.7	668.3	258.4	401.3	308.1	345.7	667.2	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155ZB550C4-425AXSP04	229.8	363.2	276	310.9	-	231.4	363.8	277.1	312	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550C4-432AXSP04	212.8	338	256	289.3	-	214.2	338.8	257	290	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155ZB550C4-525AXSP04	252.4	394	301.2	338.3	-	254.1	394.8	302.3	339.5	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155ZB550C4-532AXSP04	237.3	373.4	284.4	320.8	629.5	239	373.9	285.3	321.1	628	378	17.1							

EAW-FD155SZB550K4-625AXSP04	258.9	400.1	307.6	344.8	659.8	260.4	400.1	308.9	345.3	658.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB550K4-632AXSP06	257.2	394.6	304.1	340.2	-	257.6	393.5	303.8	339.8	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB550K5-425AXSP04	220.4	347.6	264.3	298	-	221.8	347.7	264.9	298.6	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550K5-432AXSP04	204.2	324.4	245.6	277.4	-	205.6	324.1	246.4	278.1	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550K5-525AXSP04	242.3	378.1	289	325	-	243.9	378.5	289.9	325.3	630	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550K5-532AXSP04	227.4	358.1	272.8	307.5	602.6	229.1	358.1	273.8	307.9	601.3	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550K5-625AXSP04	258.9	400.1	307.6	344.8	659.8	260.4	400.1	308.9	345.3	658.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB550K5-632AXSP06	257.2	394.6	304.1	340.2	-	257.6	393.5	303.8	339.8	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB550K8-425AXSP04	220.4	347.6	264.3	298	-	221.8	347.7	264.9	298.6	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550K8-432AXSP04	204.2	324.4	245.6	277.4	-	205.6	324.1	246.4	278.1	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550K8-525AXSP04	242.3	378.1	289	325	-	243.9	378.5	289.9	325.3	630	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550K8-532AXSP04	227.4	358.1	272.8	307.5	602.6	229.1	358.1	273.8	307.9	601.3	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550K8-625AXSP04	258.9	400.1	307.6	344.8	659.8	260.4	400.1	308.9	345.3	658.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB550K8-632AXSP06	257.2	394.6	304.1	340.2	-	257.6	393.5	303.8	339.8	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB550K9-425AXSP04	220.4	347.6	264.3	298	-	221.8	347.7	264.9	298.6	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550K9-432AXSP04	204.2	324.4	245.6	277.4	-	205.6	324.1	246.4	278.1	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550K9-525AXSP04	242.3	378.1	289	325	-	243.9	378.5	289.9	325.3	630	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550K9-532AXSP04	227.4	358.1	272.8	307.5	602.6	229.1	358.1	273.8	307.9	601.3	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550K9-625AXSP04	258.9	400.1	307.6	344.8	659.8	260.4	400.1	308.9	345.3	658.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB550K9-632AXSP06	257.2	394.6	304.1	340.2	-	257.6	393.5	303.8	339.8	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB550R3-425AXSP04	224.5	354.5	269.4	303.8	-	225.9	354.8	270.1	304.5	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550R3-432AXSP04	208.1	330.2	250.1	282.6	-	209.4	330.6	251.1	283.2	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB550R3-532AXSP04	247.3	385.5	294.5	331.2	-	248.5	385.5	295.5	331.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550R3-532AXSP04	232	365	277.9	313.3	613.8	233.4	365.2	279	313.8	612.7	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB550R3-632AXSP06	263.4	407.4	313.4	351	672.9	265.4	407.6	314.4	352	671.5	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB550R3-632AXSP06	261.8	402	309.6	346.5	-	262.4	401.3	309.5	346.3	-	304	22.8	4"	244	18	3"	365	32	4"
EAW-FD155SZB750K2-425AXSP04	232.4	367.5	279.1	314.6	-	234.1	368.3	280.4	315.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K2-432AXSP04	215.4	342.2	259.2	293.1	-	216.8	342.8	260.2	293.8	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K2-525AXSP04	255.3	398.9	304.8	342.4	-	257.2	399.8	306	343.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K2-532AXSP04	239.9	377.8	287.6	323.9	-	241.7	378.3	288.5	324.8	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K2-625AXSP04	272	420.7	323.3	362.2	695.6	274.1	421.4	324.8	363.8	694.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K2-632AXSP04	259.3	405.5	310.2	348.7	676.6	261.4	406.2	311.8	349.8	675.6	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K3-425AXSP04	232.4	367.5	279.1	314.6	-	234.1	368.3	280.4	315.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K3-432AXSP04	215.4	342.2	259.2	293.1	-	216.8	342.8	260.2	293.8	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K3-525AXSP04	255.3	398.9	304.8	342.4	-	257.2	399.8	306	343.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K3-532AXSP04	239.9	377.8	287.6	323.9	-	241.7	378.3	288.5	324.8	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K3-625AXSP04	272	420.7	323.3	362.2	695.6	274.1	421.4	324.8	363.8	694.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K3-632AXSP04	259.3	405.5	310.2	348.7	676.6	261.4	406.2	311.8	349.8	675.6	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K4-425AXSP04	232.4	367.5	279.1	314.6	-	234.1	368.3	280.4	315.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K4-432AXSP04	215.4	342.2	259.2	293.1	-	216.8	342.8	260.2	293.8	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K4-525AXSP04	255.3	398.9	304.8	342.4	-	257.2	399.8	306	343.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K4-532AXSP04	239.9	377.8	287.6	323.9	-	241.7	378.3	288.5	324.8	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K4-625AXSP04	272	420.7	323.3	362.2	695.6	274.1	421.4	324.8	363.8	694.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K4-632AXSP04	259.3	405.5	310.2	348.7	676.6	261.4	406.2	311.8	349.8	675.6	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K5-425AXSP04	232.4	367.5	279.1	314.6	-	234.1	368.3	280.4	315.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K5-432AXSP04	215.4	342.2	259.2	293.1	-	216.8	342.8	260.2	293.8	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K5-525AXSP04	255.3	398.9	304.8	342.4	-	257.2	399.8	306	343.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K5-532AXSP04	239.9	377.8	287.6	323.9	-	241.7	378.3	288.5	324.8	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K5-625AXSP04	272	420.7	323.3	362.2	695.6	274.1	421.4	324.8	363.8	694.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K5-632AXSP04	259.3	405.5	310.2	348.7	676.6	261.4	406.2	311.8	349.8	675.6	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K8-425AXSP04	232.4	367.5	279.1	314.6	-	234.1	368.3	280.4	315.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K8-432AXSP04	215.4	342.2	259.2	293.1	-	216.8	342.8	260.2	293.8	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K8-525AXSP04	255.3	398.9	304.8	342.4	-	257.2	399.8	306	343.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K8-532AXSP04	239.9	377.8	287.6	323.9	-	241.7	378.3	288.5	324.8	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K8-625AXSP04	272	420.7	323.3	362.2	695.6	274.1	421.4	324.8	363.8	694.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K8-632AXSP04	259.3	405.5	310.2	348.7	676.6	261.4	406.2	311.8	349.8	675.6	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K9-425AXSP04	232.4	367.5	279.1	314.6	-	234.1	368.3	280.4	315.7	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K9-432AXSP04	215.4	342.2	259.2	293.1	-	216.8	342.8	260.2	293.8	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZB750K9-525AXSP04	255.3	398.9	304.8	342.4	-	257.2	399.8	306	343.7	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K9-532AXSP04	239.9	377.8	287.6	323.9	-	241.7	378.3	288.5	324.8	-	378	17.1	4"	302	11.3	4"	453	20.4	(2) 4"
EAW-FD155SZB750K9-625AXSP04	272	420.7	323.3	362.2	695.6	274.1	421.4	324.8	363.8	694.9	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZB750K9-632AXSP04	259.3	405.5	310.2	348.7	676.6	261.4	406.2	311.8	349.8	675.6	456	15	(2) 4"	365	12.3	4"	548	21	(2) 4"
EAW-FD155SZK370C2-425AXSP04	227.9	359.6	273.5	308.6	-	229.5	360.3	274.5	309.6	-	304	15.9	4"	244	13.4	3"	365	22.4	4"
EAW-FD155SZK370C2-432AXSP04	211.4	335.6	254.2	287.3	-	212.7	33												

EAW-FD1555ZK370K4-532AXSP04	225.6	352.1	269.5	302.9	588.2	226.4	351.4	269.4	302.3	585.1	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK370K4-625AXSP04	256.4	392.8	303.7	338.9	643.1	257.3	391.5	303.5	338.7	640.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK370K4-632AXSP04	244.7	378.2	291	326.2	625.6	245.3	377.4	290.8	325.9	622.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK370K5-425AXSP04	218.2	340.9	260.1	293	-	218.7	340.4	260.2	292.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK370K5-432AXSP04	202.1	318.2	242.1	272.7	-	202.8	317.4	242.2	272.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK370K5-525AXSP04	240	370.9	284.7	319.5	614.7	240.7	370.3	284.7	318.9	611.9	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK370K5-532AXSP04	225.6	352.1	269.5	302.9	588.2	226.4	351.4	269.4	302.3	585.1	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK370K5-625AXSP04	256.4	392.8	303.7	338.9	643.1	257.3	391.5	303.5	338.7	640.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK370K5-632AXSP04	244.7	378.2	291	326.2	625.6	245.3	377.4	290.8	325.9	622.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK370K8-425AXSP04	218.2	340.9	260.1	293	-	218.7	340.4	260.2	292.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK370K8-432AXSP04	202.1	318.2	242.1	272.7	-	202.8	317.4	242.2	272.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK370K8-525AXSP04	240	370.9	284.7	319.5	614.7	240.7	370.3	284.7	318.9	611.9	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK370K8-532AXSP04	225.6	352.1	269.5	302.9	588.2	226.4	351.4	269.4	302.3	585.1	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK370K8-625AXSP04	256.4	392.8	303.7	338.9	643.1	257.3	391.5	303.5	338.7	640.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK370K8-632AXSP04	244.7	378.2	291	326.2	625.6	245.3	377.4	290.8	325.9	622.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400B3-425AXSP04	217.9	340.4	260.2	292.6	-	218.9	340.1	260.4	292.7	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400B3-432AXSP04	203	319.4	243	274.2	-	203.6	318.9	243.3	273.7	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400B3-525AXSP04	237.9	367.7	282.7	316.7	609.1	238.8	367.4	282.9	316.9	607.8	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400B3-532AXSP04	225.1	351.2	268.9	301.7	586.7	225.9	350.7	268.9	302.2	584.7	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400B3-625AXSP04	251.7	385.3	298	333.1	630.6	253	385.3	298.4	333	629.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400B3-632AXSP06	252	383	296.2	330.8	-	251.9	382	296.2	330.3	-	304	25	4"	244	19.4	3"	365	35	4"
EAW-FD1555ZK400C3-425AXSP04	225.1	352.4	269	302.6	-	225.9	351.7	268.9	302.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400C3-432AXSP04	208.8	329.3	250.3	282.4	-	209.6	328.8	250.5	282.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400C3-525AXSP04	247.3	382.2	293.4	328.9	-	248	382.1	293.9	329.3	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400C3-532AXSP04	232.7	363.8	278.1	312.3	608.5	234	363.2	278.1	312.7	605.4	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400C3-625AXSP04	262.9	402.5	310.9	347.6	660.1	264.1	402.2	311.6	347.8	658	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400C3-632AXSP04	251.8	389.8	299.6	336	645.2	252.8	389	299.9	335.7	643	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400C9-425AXSP04	225.1	352.4	269	302.6	-	225.9	351.7	268.9	302.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400C9-432AXSP04	208.8	329.3	250.3	282.4	-	209.6	328.8	250.5	282.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400C9-525AXSP04	247.3	382.2	293.4	328.9	-	248	382.1	293.9	329.3	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400C9-532AXSP04	232.7	363.8	278.1	312.3	608.5	234	363.2	278.1	312.7	605.4	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400C9-625AXSP04	262.9	402.5	310.9	347.6	660.1	264.1	402.2	311.6	347.8	658	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400C9-632AXSP04	251.8	389.8	299.6	336	645.2	252.8	389	299.9	335.7	643	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400K3-425AXSP04	218.2	340.9	260.1	293	-	218.7	340.4	260.2	292.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400K3-432AXSP04	202.1	318.2	242.1	272.7	-	202.8	317.4	242.2	272.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400K3-525AXSP04	240	370.9	284.7	319.5	614.7	240.7	370.3	284.7	318.9	611.9	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400K3-532AXSP04	225.6	352.1	269.5	302.9	588.2	226.4	351.4	269.4	302.3	585.1	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400K3-625AXSP04	256.4	392.8	303.7	338.9	643.1	257.3	391.5	303.5	338.7	640.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400K3-632AXSP04	244.7	378.2	291	326.2	625.6	245.3	377.4	290.8	325.9	622.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400K9-425AXSP04	218.2	340.9	260.1	293	-	218.7	340.4	260.2	292.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400K9-432AXSP04	202.1	318.2	242.1	272.7	-	202.8	317.4	242.2	272.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400K9-525AXSP04	240	370.9	284.7	319.5	614.7	240.7	370.3	284.7	318.9	611.9	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400K9-532AXSP04	225.6	352.1	269.5	302.9	588.2	226.4	351.4	269.4	302.3	585.1	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400K9-625AXSP04	256.4	392.8	303.7	338.9	643.1	257.3	391.5	303.5	338.7	640.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400K9-632AXSP04	244.7	378.2	291	326.2	625.6	245.3	377.4	290.8	325.9	622.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400R3-425AXSP04	220.8	345.3	263.8	296.7	-	221.5	345	264.1	296.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400R3-432AXSP04	204.8	322.4	245.4	276.7	-	205.4	322.3	245.6	276.6	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK400R3-525AXSP04	242.9	375.7	288.2	323.5	622.8	243.8	374.7	288.4	323	620.2	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400R3-632AXSP04	228.5	356.8	273	306.4	596.3	229.1	355.9	272.7	306.5	593.7	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK400R3-625AXSP04	259.7	397.4	307.1	343.3	651.6	260.3	396.3	307.1	342.7	648.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK400R3-632AXSP04	247.6	383	294.5	330.2	633.6	248.3	382.3	294.5	330.1	630.7	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK500B3-425AXSP04	235.4	368.9	280.9	316.3	-	236.3	369	281.6	316.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK500B3-432AXSP04	218.8	345.1	262.2	295.7	-	219.6	345.3	262.9	296	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK500B3-525AXSP04	257.2	398.2	305.3	342.4	-	258.5	398.5	306	343.1	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK500B3-532AXSP04	243	379.5	290	325.9	-	244.5	379.8	290.7	326.6	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK500B3-625AXSP04	272.2	417.2	322	359.7	684.8	273.6	417.3	322.9	360.6	684.1	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK500B3-632AXSP04	261.7	405.2	311.5	349.7	671.5	263.1	405.5	312.2	349.7	670.1	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550C2-425AXSP04	249.4	391.9	298.7	336	-	250.4	391.7	299.1	336.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550C2-432AXSP04	230.5	364.4	276.6	312.3	-	231.4	364.2	277	312.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550C2-525AXSP04	275.1	427	327	367.1	-	276.4	426.9	328	367.5	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550C2-532AXSP04	258.2	404.1	308.5	347	-	259.4	403.8	308.8	347.2	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550C2-625AXSP04	294	451.6	348.2	389.2	743.6	295.8	451.8	348.8	389.9	742	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550C2-632AXSP04	280.5	435	333.6	374.1	72														

EAW-FD1555ZK550K3-525AXSP04	262.9	407.7	312.8	350.8	-	264.2	407.6	313.3	350.8	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K3-532AXSP04	247.4	386.1	294.8	331.9	-	248.4	386.2	295.4	332	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K3-532AXSP04	282.1	432.5	333.4	373.1	711.4	283.1	431.7	333.7	372.8	708.3	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K3-632AXSP04	268.4	415.4	319	358.1	689.8	269.1	415.2	319.4	357.8	686.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K4-425AXSP04	238.9	374.8	285.3	321.3	-	239.6	374.4	286	321.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550K4-432AXSP04	220.9	348.7	265.1	299	-	221.6	348.3	265.3	298.8	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550K4-525AXSP04	262.9	407.7	312.8	350.8	-	264.2	407.6	313.3	350.8	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K4-532AXSP04	247.4	386.1	294.8	331.9	-	248.4	386.2	295.4	332	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K4-625AXSP04	282.1	432.5	333.4	373.1	711.4	283.1	431.7	333.7	372.8	708.3	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K4-632AXSP04	268.4	415.4	319	358.1	689.8	269.1	415.2	319.4	357.8	686.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K5-425AXSP04	238.9	374.8	285.3	321.3	-	239.6	374.4	286	321.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550K5-432AXSP04	220.9	348.7	265.1	299	-	221.6	348.3	265.3	298.8	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550K5-525AXSP04	262.9	407.7	312.8	350.8	-	264.2	407.6	313.3	350.8	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K5-532AXSP04	247.4	386.1	294.8	331.9	-	248.4	386.2	295.4	332	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K5-625AXSP04	282.1	432.5	333.4	373.1	711.4	283.1	431.7	333.7	372.8	708.3	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K5-632AXSP04	268.4	415.4	319	358.1	689.8	269.1	415.2	319.4	357.8	686.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K9-425AXSP04	238.9	374.8	285.3	321.3	-	239.6	374.4	286	321.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550K9-432AXSP04	220.9	348.7	265.1	299	-	221.6	348.3	265.3	298.8	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550K9-525AXSP04	262.9	407.7	312.8	350.8	-	264.2	407.6	313.3	350.8	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K9-532AXSP04	247.4	386.1	294.8	331.9	-	248.4	386.2	295.4	332	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550K9-625AXSP04	282.1	432.5	333.4	373.1	711.4	283.1	431.7	333.7	372.8	708.3	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K9-632AXSP04	268.4	415.4	319	358.1	689.8	269.1	415.2	319.4	357.8	686.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550R3-425AXSP04	243.5	382.3	291.2	328.1	-	244.7	382.2	291.6	328.4	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550R3-432AXSP04	225.4	355.7	270.3	305.1	-	226.3	355.5	270.6	305.1	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK550R3-525AXSP04	268.2	416.3	319.1	358.1	-	269.6	415.8	319.3	358.2	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550R3-532AXSP04	252.3	394.2	300.7	338.7	-	252.9	393.8	301.5	338.9	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK550R3-625AXSP04	287.7	441.4	340.1	380.6	726.4	288.9	440.7	340.5	380.5	723.5	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550R3-632AXSP04	273.6	423.9	325.3	365.3	703.5	274.5	423.9	325.8	365.2	701.3	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK550K4-425AXSP04	260.1	409.7	311.7	351.5	-	261.6	409.6	312.6	351.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750C4-432AXSP04	240.8	381.1	289.3	326.6	-	242.1	381.7	290.1	327.1	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750C4-525AXSP04	285.5	444.1	340.1	382	-	287.5	445	341.3	383.3	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750C4-532AXSP04	268.7	420.9	321.3	361.7	-	270.1	421.5	322.3	362.1	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750C4-632AXSP04	291	451.5	346.2	388.5	752	292.7	452.2	347.3	389.5	750.7	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K5-425AXSP04	260.1	409.7	311.7	351.5	-	261.6	409.6	312.6	351.9	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750C5-432AXSP04	240.8	381.1	289.3	326.6	-	242.1	381.7	290.1	327.1	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K5-525AXSP04	285.5	444.1	340.1	382	-	287.5	445	341.3	383.3	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750C5-532AXSP04	268.7	420.9	321.3	361.7	-	270.1	421.5	322.3	362.1	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750C5-632AXSP04	291	451.5	346.2	388.5	752	292.7	452.2	347.3	389.5	750.7	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K2-425AXSP04	252.8	397.2	302.5	341.1	-	254	397.6	303.4	341.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K2-432AXSP04	234.1	370.6	281.1	317.1	-	235	370.1	281.5	317.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K2-525AXSP04	278	432.4	331	371.7	-	279.8	432.4	331.6	372.2	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K2-532AXSP04	261.5	408.9	311.9	351.6	-	262.5	409	313.1	351.6	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K2-625AXSP04	297.7	457.4	352.6	394.2	753.5	299.6	457.8	353.3	395	752.1	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K2-632AXSP04	283.8	439.8	337.6	378.6	731.8	285	440.2	337.9	378.9	729.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K3-425AXSP04	252.8	397.2	302.5	341.1	-	254	397.6	303.4	341.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K3-432AXSP04	234.1	370.6	281.1	317.1	-	235	370.1	281.5	317.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K3-525AXSP04	278	432.4	331	371.7	-	279.8	432.4	331.6	372.2	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K3-532AXSP04	261.5	408.9	311.9	351.6	-	262.5	409	313.1	351.6	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K3-625AXSP04	297.7	457.4	352.6	394.2	753.5	299.6	457.8	353.3	395	752.1	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K3-632AXSP04	283.8	439.8	337.6	378.6	731.8	285	440.2	337.9	378.9	729.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K4-425AXSP04	252.8	397.2	302.5	341.1	-	254	397.6	303.4	341.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K4-432AXSP04	234.1	370.6	281.1	317.1	-	235	370.1	281.5	317.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K4-525AXSP04	278	432.4	331	371.7	-	279.8	432.4	331.6	372.2	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K4-532AXSP04	261.5	408.9	311.9	351.6	-	262.5	409	313.1	351.6	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K4-625AXSP04	297.7	457.4	352.6	394.2	753.5	299.6	457.8	353.3	395	752.1	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K4-632AXSP04	283.8	439.8	337.6	378.6	731.8	285	440.2	337.9	378.9	729.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K5-425AXSP04	252.8	397.2	302.5	341.1	-	254	397.6	303.4	341.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K5-432AXSP04	234.1	370.6	281.1	317.1	-	235	370.1	281.5	317.5	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K5-525AXSP04	278	432.4	331	371.7	-	279.8	432.4	331.6	372.2	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K5-532AXSP04	261.5	408.9	311.9	351.6	-	262.5	409	313.1	351.6	-	378	18.5	4"	302	12.2	4"	453	22.4	(2) 4"
EAW-FD1555ZK750K5-625AXSP04	297.7	457.4	352.6	394.2	753.5	299.6	457.8	353.3	395	752.1	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K5-632AXSP04	283.8	439.8	337.6	378.6	731.8	285	440.2	337.9	378.9	729.2	456	16.4	(2) 4"	365	13.2	4"	548	23	(2) 4"
EAW-FD1555ZK750K8-425AXSP04	252.8	397.2	302.5	341.1	-	254	397.6	303.4	341.3	-	304	17.4	4"	244	14.4	3"	365	24.4	4"
EAW-FD1555ZK750K8-																			

EAW-FD15S6PB400C9-532AXSP04	242	376.8	288.4	324.1	-	243.3	377.5	288.9	324.5	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400C9-625AXSP04	268	409.2	316.2	353.2	671	270.1	410.2	317.3	354.4	671.8	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400C9-632AXSP04	258.8	398.9	306.5	343.5	660.4	260.1	399.3	307.7	344.7	660.1	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400K3-425AXSP04	228.3	357	272.5	306.8	-	229.2	357	273	306.6	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB400K3-432AXSP04	212	333.6	253.8	286.1	-	212.8	333.7	254.1	286.4	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB400K3-525AXSP04	251.6	388.8	298.2	334.4	-	252.7	388.6	299.1	334.7	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400K3-532AXSP04	237.3	369.6	282.7	317.6	-	238	369.4	282.9	317.8	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400K3-625AXSP04	267.5	407.9	315.2	352.5	669.6	268.4	407.6	315.8	352.2	667.5	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400K3-632AXSP04	255.8	394.2	303	339.5	652.3	256.8	393.9	303.7	339.6	650.8	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400K9-425AXSP04	228.3	357	272.5	306.8	-	229.2	357	273	306.6	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB400K9-432AXSP04	212	333.6	253.8	286.1	-	212.8	333.7	254.1	286.4	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB400K9-525AXSP04	251.6	388.8	298.2	334.4	-	252.7	388.6	299.1	334.7	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400K9-532AXSP04	237.3	369.6	282.7	317.6	-	238	369.4	282.9	317.8	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400K9-625AXSP04	267.5	407.9	315.2	352.5	669.6	268.4	407.6	315.8	352.2	667.5	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400K9-632AXSP04	255.8	394.2	303	339.5	652.3	256.8	393.9	303.7	339.6	650.8	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400R3-425AXSP04	230.6	360.9	275.3	310	-	231.6	361	275.9	309.9	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB400R3-432AXSP04	214.1	337.2	256.7	289.2	-	215	337.6	257.2	289.6	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB400R3-525AXSP04	253.7	392.2	301.2	337.8	-	254.9	392.3	301.7	338.3	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400R3-532AXSP04	239.6	373.4	285.4	320.7	-	240.3	373.3	285.8	321	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB400R3-625AXSP04	270	411.7	318.1	355.8	676	271	411.6	318.4	355.6	674.2	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB400R3-632AXSP04	257.9	398.1	306	342.8	659	258.9	398	306.3	343.1	656.9	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550B3-425AXSP02	210.9	351.3	260.7	298	606.2	215.6	354.7	264.5	301.6	608.1	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550B3-432AXSP04	224.9	354.5	269.6	304	-	226.2	355.5	270.6	305	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB550B3-525AXSP02	-	-	-	-	-	-	-	-	-	-	676	10.8	(2) 4"	541	7.1	(2) 4"	812	15.2	(2) 4"
EAW-FD15S6PB550B3-532AXSP04	-	-	-	-	-	250.4	389.1	297.9	334.9	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	12	(2) 4"	649	7.9	(2) 4"	974	13.8	(3) 4"
EAW-FD15S6PB550B3-632AXSP02	-	-	-	-	-	-	-	-	-	-	812	12	(2) 4"	649	7.9	(2) 4"	974	13.8	(3) 4"
EAW-FD15S6PB550C3-425AXSP02	226.1	377	279.9	319.9	650.9	230.9	379.6	283.6	323.1	652.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550C3-432AXSP02	208.5	350.9	259.2	296.9	609.4	213.1	353.8	262.6	300	610.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550C3-525AXSP04	282.5	437.8	335.9	376.6	-	284.5	439.5	337.2	378	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550C3-532AXSP04	266.4	416.7	318	358	-	268.3	417.3	319.6	359	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550C3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	12	(2) 4"	649	7.9	(2) 4"	974	13.8	(3) 4"
EAW-FD15S6PB550C3-632AXSP04	-	-	-	-	-	288	443.7	341.1	382.7	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550C9-425AXSP02	226.1	377	279.9	319.9	650.9	230.9	379.6	283.6	323.1	652.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550C9-432AXSP02	208.5	350.9	259.2	296.9	609.4	213.1	353.8	262.6	300	610.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550C9-525AXSP04	282.5	437.8	335.9	376.6	-	284.5	439.5	337.2	378	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550C9-532AXSP04	266.4	416.7	318	358	-	268.3	417.3	319.6	359	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550C9-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	12	(2) 4"	649	7.9	(2) 4"	974	13.8	(3) 4"
EAW-FD15S6PB550C9-632AXSP04	-	-	-	-	-	288	443.7	341.1	382.7	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550K3-425AXSP02	217.5	362.3	268.9	307.6	625.2	221.8	364.6	272.2	310.2	626.2	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550K3-432AXSP04	229.6	362.7	275.3	310.7	-	230.9	362.6	276.2	311.3	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB550K3-625AXSP04	273.2	423.4	324.7	363.9	-	274.5	423.3	325.7	365	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550K3-632AXSP04	257.4	401.6	307	345.4	-	258.6	402	307.8	345.6	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550K3-625AXSP04	290.3	444.7	343.2	383.7	-	291.8	445.1	344	384.6	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550K3-632AXSP04	277.5	428.7	329	369	-	278.6	429.1	329.9	369.9	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550K9-425AXSP02	217.5	362.3	268.9	307.6	625.2	221.8	364.6	272.2	310.2	626.2	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550K9-432AXSP04	229.6	362.7	275.3	310.7	-	230.9	362.6	276.2	311.3	-	270	18	4"	216	14.2	3"	325	25.3	4"
EAW-FD15S6PB550K9-525AXSP04	273.2	423.4	324.7	363.9	-	274.5	423.3	325.7	365	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550K9-532AXSP04	257.4	401.6	307	345.4	-	258.6	402	307.8	345.6	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550K9-625AXSP04	290.3	444.7	343.2	383.7	-	291.8	445.1	344	384.6	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550K9-632AXSP04	277.5	428.7	329	369	-	278.6	429.1	329.9	369.9	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550R3-425AXSP02	221.4	369.4	273.9	313.1	637.1	225.9	371.3	277.2	315.9	637.3	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550R3-432AXSP02	204.1	343.4	253.5	290.5	596.5	208.4	345.5	256.8	293.2	597	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB550R3-525AXSP04	277.6	430.6	330	370.6	-	279	431.4	331.2	371.2	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550R3-532AXSP04	261.4	409	311.9	351	-	262.9	409.2	313.1	351.6	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB550R3-625AXSP04	295.3	452.6	348.7	390.5	-	296.9	452.6	349.7	390.9	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB550R3-632AXSP04	281.8	435.7	334.8	375.5	-	283.5	436.3	335.7	375.9	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB750K3-425AXSP02	228.7	381.2	282.8	323.7	657.6	233.6	384	286.7	327.1	660.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB750K3-432AXSP02	210.9	354.9	262	300.2	616.2	215.4	357.5	265.4	303.4	617.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB750K3-525AXSP04	285.7	443.9	339.8	381.7	-	287.5	444.6	341.4	382.8	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB750K3-532AXSP04	269.2	421.4	321.4	361.9	-	271.2	422.1	323.1	363	-	338	19	4"	270	12.5	4"	406	26.7	4"
EAW-FD15S6PB750K3-625AXSP04	303.6	465.9	358.6	401.7	-	305.2	466.4	360	402.6	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB750K3-632AXSP04	290.1	449.1	344.1	386.2	-	291.7	449.6	345.5	387.1	-	406	20.2	4"	325	13.3	4"	487	24.2	(2) 4"
EAW-FD15S6PB750K9-425AXSP02	228.7	381.2	282.8	323.7	657.6	233.6	384	286.7	327.1	660.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB750K9-432AXSP02	210.9	354.9	262	300.2	616.2	215.4	357.5	265.4	303.4	617.4	541	9.8	(2) 4"	433	9.8	4"	649	13.8	(2) 4"
EAW-FD15S6PB750K9-525AXSP04	285.7	443.9</																	

EAW-FD15S6ZB370K2-525AXSP04	270.9	418.1	321.5	360.3	-	272	417.8	321.4	360.1	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K2-532AXSP04	255.5	397.3	304.2	341.6	-	256.3	396.5	304.1	341.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K2-625AXSP04	289.8	442.4	341.8	381.6	724.8	290.8	441.6	342.1	381.4	721.8	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K2-632AXSP04	276.8	426.4	328.2	367.5	704.9	277.3	425.4	328.4	367.1	702.1	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K4-425AXSP04	246.3	384.9	294.3	331.1	-	247.3	384.4	294.4	330.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB370K4-432AXSP04	228.8	360	274	308.8	-	229.5	359.5	274.2	308.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB370K4-525AXSP04	270.9	418.1	321.5	360.3	-	272	417.8	321.4	360.1	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K4-532AXSP04	255.5	397.3	304.2	341.6	-	256.3	396.5	304.1	341.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K4-625AXSP04	289.8	442.4	341.8	381.6	724.8	290.8	441.6	342.1	381.4	721.8	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K4-632AXSP04	276.8	426.4	328.2	367.5	704.9	277.3	425.4	328.4	367.1	702.1	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K5-425AXSP04	246.3	384.9	294.3	331.1	-	247.3	384.4	294.4	330.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB370K5-432AXSP04	228.8	360	274	308.8	-	229.5	359.5	274.2	308.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB370K5-525AXSP04	270.9	418.1	321.5	360.3	-	272	417.8	321.4	360.1	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K5-532AXSP04	255.5	397.3	304.2	341.6	-	256.3	396.5	304.1	341.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K5-625AXSP04	289.8	442.4	341.8	381.6	724.8	290.8	441.6	342.1	381.4	721.8	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K5-632AXSP04	276.8	426.4	328.2	367.5	704.9	277.3	425.4	328.4	367.1	702.1	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K8-425AXSP04	246.3	384.9	294.3	331.1	-	247.3	384.4	294.4	330.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB370K8-432AXSP04	228.8	360	274	308.8	-	229.5	359.5	274.2	308.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB370K8-525AXSP04	270.9	418.1	321.5	360.3	-	272	417.8	321.4	360.1	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K8-532AXSP04	255.5	397.3	304.2	341.6	-	256.3	396.5	304.1	341.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB370K8-625AXSP04	289.8	442.4	341.8	381.6	724.8	290.8	441.6	342.1	381.4	721.8	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB370K8-632AXSP04	276.8	426.4	328.2	367.5	704.9	277.3	425.4	328.4	367.1	702.1	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400B3-425AXSP04	245	382.6	292.1	328.5	-	246	382.9	292.8	329.3	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400B3-432AXSP04	228.5	359.2	273.6	308.1	-	229.4	359.4	274	308.7	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400B3-525AXSP04	266.6	411	315.8	353.9	-	267.8	411	316.7	354.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400B3-532AXSP04	253.2	393.4	301.4	338.3	-	254.2	393.7	302	339	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	913	10.3	(3) 4"	730	8.5	(2) 4"	1096	14.5	(3) 4"
EAW-FD15S6ZB400B3-632AXSP04	271.7	418.8	322.6	361.1	691.9	273	419.1	323.3	361.3	690.5	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400C3-425AXSP04	253.6	396.3	302.6	340.6	-	254.6	396.4	303.2	340.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400C3-432AXSP04	236	371	282.4	318.3	-	236.7	370.9	282.6	318.3	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400C3-525AXSP04	277.1	428	328.9	368.7	-	278.5	428.3	329.6	369.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400C3-532AXSP04	262.5	408.1	312.6	351.2	-	263.3	407.9	313	351.5	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400C3-625AXSP04	294.3	448.9	347.1	387.6	735.7	295.9	449	348.1	388.1	735	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400C3-632AXSP04	283.1	435.8	335.7	376	721.9	284.3	435.8	336.2	376	719.9	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400C9-425AXSP04	253.6	396.3	302.6	340.6	-	254.6	396.4	303.2	340.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400C9-432AXSP04	236	371	282.4	318.3	-	236.7	370.9	282.6	318.3	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400C9-525AXSP04	277.1	428	328.9	368.7	-	278.5	428.3	329.6	369.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400C9-532AXSP04	262.5	408.1	312.6	351.2	-	263.3	407.9	313	351.5	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400C9-625AXSP04	294.3	448.9	347.1	387.6	735.7	295.9	449	348.1	388.1	735	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400C9-632AXSP04	283.1	435.8	335.7	376	721.9	284.3	435.8	336.2	376	719.9	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400K3-425AXSP04	246.3	384.9	294.3	331.1	-	247.3	384.4	294.4	330.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400K3-432AXSP04	228.8	360	274	308.8	-	229.5	359.5	274.2	308.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400K3-525AXSP04	270.9	418.1	321.5	360.3	-	272	417.8	321.4	360.1	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400K3-532AXSP04	255.5	397.3	304.2	341.6	-	256.3	396.5	304.1	341.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400K3-625AXSP04	289.8	442.4	341.8	381.6	724.8	290.8	441.6	342.1	381.4	721.8	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400K3-632AXSP04	276.8	426.4	328.2	367.5	704.9	277.3	425.4	328.4	367.1	702.1	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400K9-425AXSP04	246.3	384.9	294.3	331.1	-	247.3	384.4	294.4	330.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400K9-432AXSP04	228.8	360	274	308.8	-	229.5	359.5	274.2	308.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400K9-525AXSP04	270.9	418.1	321.5	360.3	-	272	417.8	321.4	360.1	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400K9-532AXSP04	255.5	397.3	304.2	341.6	-	256.3	396.5	304.1	341.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400K9-625AXSP04	289.8	442.4	341.8	381.6	724.8	290.8	441.6	342.1	381.4	721.8	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400K9-632AXSP04	276.8	426.4	328.2	367.5	704.9	277.3	425.4	328.4	367.1	702.1	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400R3-425AXSP04	249.2	389.7	297.8	334.5	-	250.4	389.3	298.1	334.7	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400R3-432AXSP04	231.7	364.1	277.5	312.6	-	232.5	363.9	277.6	312.5	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB400R3-525AXSP04	274.3	422.8	325	364.3	-	275.1	422.7	325	364.2	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400R3-532AXSP04	258.4	402	307.6	345.5	-	258.9	401.4	307.7	345.5	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB400R3-625AXSP04	292.9	446.7	345.5	385.7	731.9	293.6	446.1	345.4	385.7	729.2	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB400R3-632AXSP04	279.7	431.1	331.7	371.5	712.8	280.8	430.8	332	371.7	710.3	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB50B3-425AXSP04	263.5	412.7	314.6	354.3	-	265.1	413	315.3	355.1	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB50B3-432AXSP04	245.4	387	294.2	331.6	-	246.7	387	294.8	332.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB50B3-525AXSP04	286.4	442.5	340.1	381.5	-	288.1	443.7	341	382.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB50B3-532AXSP04	271.6	423.9	323.7	363.8	-	273.3	424.3	325.1	364.6	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB50B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	913	10.3	(3) 4"	730	8.5	(2) 4"	1096	14.5	(3) 4"
EAW-FD15S6ZB50B3-632AXSP04	-	-	-	-	-	293.6	451.3	347.3	389.1	745.2	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550C2-425AXSP02	246.1	410.																	

EAW-FD15S6ZB550K2-432AXSP04	249.2	393.1	298.6	336.7	-	250.3	392.7	299.2	337.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550K2-525AXSP04	295.9	457.9	351.5	394.4	-	297.1	457.6	351.9	394.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K2-532AXSP04	278.2	434.1	331.6	372.9	-	279.1	433.9	332.1	373.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K2-625AXSP04	316.9	484	374	418	-	318.1	484	374.5	418.4	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K2-632AXSP04	302.1	466.6	358.6	402	-	303.2	466.2	358.8	402.2	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K3-425AXSP02	235.6	392.7	291.5	333.2	677.3	240.1	395.4	294.7	335.7	677.5	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB550K3-432AXSP04	249.2	393.1	298.6	336.7	-	250.3	392.7	299.2	337.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550K3-525AXSP04	295.9	457.9	351.5	394.4	-	297.1	457.6	351.9	394.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K3-532AXSP04	278.2	434.1	331.6	372.9	-	279.1	433.9	332.1	373.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K3-625AXSP04	316.9	484	374	418	-	318.1	484	374.5	418.4	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K3-632AXSP04	302.1	466.6	358.6	402	-	303.2	466.2	358.8	402.2	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K4-425AXSP02	235.6	392.7	291.5	333.2	677.3	240.1	395.4	294.7	335.7	677.5	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB550K4-432AXSP04	249.2	393.1	298.6	336.7	-	250.3	392.7	299.2	337.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550K4-525AXSP04	295.9	457.9	351.5	394.4	-	297.1	457.6	351.9	394.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K4-532AXSP04	278.2	434.1	331.6	372.9	-	279.1	433.9	332.1	373.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K4-625AXSP04	316.9	484	374	418	-	318.1	484	374.5	418.4	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K4-632AXSP04	302.1	466.6	358.6	402	-	303.2	466.2	358.8	402.2	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K5-425AXSP02	235.6	392.7	291.5	333.2	677.3	240.1	395.4	294.7	335.7	677.5	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB550K5-432AXSP04	249.2	393.1	298.6	336.7	-	250.3	392.7	299.2	337.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550K5-432AXSP04	295.9	457.9	351.5	394.4	-	297.1	457.6	351.9	394.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K5-532AXSP04	278.2	434.1	331.6	372.9	-	279.1	433.9	332.1	373.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K5-625AXSP04	316.9	484	374	418	-	318.1	484	374.5	418.4	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K5-632AXSP04	302.1	466.6	358.6	402	-	303.2	466.2	358.8	402.2	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K8-425AXSP02	235.6	392.7	291.5	333.2	677.3	240.1	395.4	294.7	335.7	677.5	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB550K8-432AXSP04	249.2	393.1	298.6	336.7	-	250.3	392.7	299.2	337.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550K8-525AXSP04	295.9	457.9	351.5	394.4	-	297.1	457.6	351.9	394.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K8-532AXSP04	278.2	434.1	331.6	372.9	-	279.1	433.9	332.1	373.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K8-625AXSP04	316.9	484	374	418	-	318.1	484	374.5	418.4	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K8-632AXSP04	302.1	466.6	358.6	402	-	303.2	466.2	358.8	402.2	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K9-425AXSP02	235.6	392.7	291.5	333.2	677.3	240.1	395.4	294.7	335.7	677.5	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB550K9-432AXSP04	249.2	393.1	298.6	336.7	-	250.3	392.7	299.2	337.2	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550K9-525AXSP04	295.9	457.9	351.5	394.4	-	297.1	457.6	351.9	394.8	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K9-532AXSP04	278.2	434.1	331.6	372.9	-	279.1	433.9	332.1	373.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550K9-625AXSP04	316.9	484	374	418	-	318.1	484	374.5	418.4	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550K9-632AXSP04	302.1	466.6	358.6	402	-	303.2	466.2	358.8	402.2	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550R3-425AXSP02	240.3	400.3	297.1	339.8	690.1	245	403.3	300.6	342.3	690.6	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB550R3-432AXSP04	253.7	400	304.2	343.1	-	255	400.6	304.9	343.4	-	304	18.5	4"	244	15.1	3"	365	26	4"
EAW-FD15S6ZB550R3-525AXSP04	301.4	466.9	358.2	402	-	302.8	466.8	358.7	402.5	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550R3-532AXSP04	283.3	442.5	337.8	380	-	284.3	441.8	338.5	379.9	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB550R3-625AXSP04	322.4	493.5	380.6	425.4	-	323.8	493.7	381.2	426.1	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB550R3-632AXSP04	307.5	475.3	365.1	409.4	-	308.8	475.3	365.6	409.8	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K2-425AXSP02	248.9	415.4	307.9	352	716.2	253.9	418.2	311.9	355.5	717.6	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K2-432AXSP02	229.4	385.9	284.9	326.5	670.4	234.2	388.6	288.6	329.5	670.8	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K2-525AXSP04	311.3	483.1	370.1	415.7	-	312.9	484.1	371.5	416.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K2-532AXSP04	293.1	458	349.7	393.6	-	294.5	457.8	350.1	394	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K2-625AXSP04	332.5	509.7	392.7	439.7	-	334.4	509.9	393.9	440.3	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K2-632AXSP04	317.6	491	376.6	422.5	-	319	491.8	377.8	423.7	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K3-425AXSP02	248.9	415.4	307.9	352	716.2	253.9	418.2	311.9	355.5	717.6	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K3-432AXSP02	229.4	385.9	284.9	326.5	670.4	234.2	388.6	288.6	329.5	670.8	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K3-525AXSP04	311.3	483.1	370.1	415.7	-	312.9	484.1	371.5	416.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K3-532AXSP04	293.1	458	349.7	393.6	-	294.5	457.8	350.1	394	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K3-625AXSP04	332.5	509.7	392.7	439.7	-	334.4	509.9	393.9	440.3	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K3-632AXSP04	317.6	491	376.6	422.5	-	319	491.8	377.8	423.7	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K4-425AXSP02	248.9	415.4	307.9	352	716.2	253.9	418.2	311.9	355.5	717.6	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K4-432AXSP02	229.4	385.9	284.9	326.5	670.4	234.2	388.6	288.6	329.5	670.8	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K4-525AXSP04	311.3	483.1	370.1	415.7	-	312.9	484.1	371.5	416.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K4-532AXSP04	293.1	458	349.7	393.6	-	294.5	457.8	350.1	394	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K4-625AXSP04	332.5	509.7	392.7	439.7	-	334.4	509.9	393.9	440.3	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K4-632AXSP04	317.6	491	376.6	422.5	-	319	491.8	377.8	423.7	-	456	17.5	(2) 4"	365	14	4"	548	24.6	(2) 4"
EAW-FD15S6ZB750K5-425AXSP02	248.9	415.4	307.9	352	716.2	253.9	418.2	311.9	355.5	717.6	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K5-432AXSP02	229.4	385.9	284.9	326.5	670.4	234.2	388.6	288.6	329.5	670.8	609	10.3	(2) 4"	487	6.8	(2) 4"	730	14.5	(2) 4"
EAW-FD15S6ZB750K5-525AXSP04	311.3	483.1	370.1	415.7	-	312.9	484.1	371.5	416.4	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K5-532AXSP04	293.1	458	349.7	393.6	-	294.5	457.8	350.1	394	-	378	19.7	4"	302	13	4"	453	24	(2) 4"
EAW-FD15S6ZB750K5-625AXSP04	332.5	509.7	392.7	439.7	-														


EAW-FD1556ZK370C8-425AXSP02	243.7	400.8	299.2	340.4	684.5	247.4	401.8	301.5	342.5	683.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK370C8-432AXSP04	254.4	398.8	303.8	342.3	-	254.7	397.4	303.9	341.6	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370C8-525AXSP04	301.1	462.6	356.1	398.9	-	301.4	461.8	356	398.2	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370C8-532AXSP04	283.9	440.1	337.2	378.5	-	284.3	439.3	337.2	378.4	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370C8-625AXSP04	320.5	486.7	376.8	420.6	-	321.4	486.3	377	420.8	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370C8-632AXSP04	307.5	471.7	363.4	406.8	-	308.2	470.7	363.2	406.5	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K2-425AXSP04	265.3	412.4	316.1	354.6	-	265.9	411.8	315.6	354	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K2-432AXSP04	246.1	385.3	294.1	331.1	-	246.4	384.3	293.7	330	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K2-525AXSP04	292.2	449	345.4	386.9	-	292.5	447.5	345.4	386.1	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K2-532AXSP04	275.1	426.5	326.7	366.6	-	275.5	424.9	326.6	365.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K2-625AXSP04	313	475	368	410.6	-	313.5	473.4	367.7	409.7	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K2-632AXSP04	299.2	457.7	352.9	394.9	754.6	299.4	456.7	352.7	394	749.8	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K4-525AXSP04	265.3	412.4	316.1	354.6	-	265.9	411.8	315.6	354	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K4-432AXSP04	246.1	385.3	294.1	331.1	-	246.4	384.3	293.7	330	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K4-532AXSP04	292.2	449	345.4	386.9	-	292.5	447.5	345.4	386.1	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K4-532AXSP04	275.1	426.5	326.7	366.6	-	275.5	424.9	326.6	365.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K4-625AXSP04	313	475	368	410.6	-	313.5	473.4	367.7	409.7	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K4-632AXSP04	299.2	457.7	352.9	394.9	754.6	299.4	456.7	352.7	394	749.8	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K5-425AXSP04	265.3	412.4	316.1	354.6	-	265.9	411.8	315.6	354	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K5-432AXSP04	246.1	385.3	294.1	331.1	-	246.4	384.3	293.7	330	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K5-525AXSP04	292.2	449	345.4	386.9	-	292.5	447.5	345.4	386.1	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K5-532AXSP04	275.1	426.5	326.7	366.6	-	275.5	424.9	326.6	365.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K5-625AXSP04	313	475	368	410.6	-	313.5	473.4	367.7	409.7	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K5-632AXSP04	299.2	457.7	352.9	394.9	754.6	299.4	456.7	352.7	394	749.8	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K8-425AXSP04	265.3	412.4	316.1	354.6	-	265.9	411.8	315.6	354	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K8-432AXSP04	246.1	385.3	294.1	331.1	-	246.4	384.3	293.7	330	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK370K8-525AXSP04	292.2	449	345.4	386.9	-	292.5	447.5	345.4	386.1	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K8-532AXSP04	275.1	426.5	326.7	366.6	-	275.5	424.9	326.6	365.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK370K8-625AXSP04	313	475	368	410.6	-	313.5	473.4	367.7	409.7	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK370K8-632AXSP04	299.2	457.7	352.9	394.9	754.6	299.4	456.7	352.7	394	749.8	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400B3-425AXSP04	265.5	412.6	315.7	354.8	-	266.1	411.4	315.9	354.3	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400B3-432AXSP04	247	386.8	295.1	332.3	-	247.6	386.2	295.1	331.6	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400B3-525AXSP04	289.7	445	343	383.5	-	290.7	444.6	342.7	383.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400B3-532AXSP04	274.5	424.8	326	365.7	-	275	424.1	326	365.6	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400B3-625AXSP04	307.7	465.9	361.1	402.9	760.4	308.4	465.9	361.4	403.4	758.6	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400B3-632AXSP04	296.4	453.9	350.1	391.7	747.1	296.8	452.8	350.2	391.2	744.3	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400C3-425AXSP02	243.7	400.8	299.2	340.4	684.5	247.4	401.8	301.5	342.5	683.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK400C3-432AXSP04	254.4	398.8	303.8	342.3	-	254.7	397.4	303.9	341.6	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400C3-525AXSP04	301.1	462.6	356.1	398.9	-	301.4	461.8	356	398.2	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400C3-532AXSP04	283.9	440.1	337.2	378.5	-	284.3	439.3	337.2	378.4	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400C3-625AXSP04	320.5	486.7	376.8	420.6	-	321.4	486.3	377	420.8	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400C3-632AXSP04	307.5	471.7	363.4	406.8	-	308.2	470.7	363.2	406.5	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400C9-425AXSP02	243.7	400.8	299.2	340.4	684.5	247.4	401.8	301.5	342.5	683.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK400C9-432AXSP04	254.4	398.8	303.8	342.3	-	254.7	397.4	303.9	341.6	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400C9-525AXSP04	301.1	462.6	356.1	398.9	-	301.4	461.8	356	398.2	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400C9-532AXSP04	283.9	440.1	337.2	378.5	-	284.3	439.3	337.2	378.4	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400C9-625AXSP04	320.5	486.7	376.8	420.6	-	321.4	486.3	377	420.8	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400C9-632AXSP04	307.5	471.7	363.4	406.8	-	308.2	470.7	363.2	406.5	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400K3-425AXSP04	265.3	412.4	316.1	354.6	-	265.9	411.8	315.6	354	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400K3-432AXSP04	246.1	385.3	294.1	331.1	-	246.4	384.3	293.7	330	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400K3-525AXSP04	292.2	449	345.4	386.9	-	292.5	447.5	345.4	386.1	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400K3-532AXSP04	275.1	426.5	326.7	366.6	-	275.5	424.9	326.6	365.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400K3-625AXSP04	313	475	368	410.6	-	313.5	473.4	367.7	409.7	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400K3-632AXSP04	299.2	457.7	352.9	394.9	754.6	299.4	456.7	352.7	394	749.8	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400K9-425AXSP04	265.3	412.4	316.1	354.6	-	265.9	411.8	315.6	354	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400K9-432AXSP04	246.1	385.3	294.1	331.1	-	246.4	384.3	293.7	330	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400K9-525AXSP04	292.2	449	345.4	386.9	-	292.5	447.5	345.4	386.1	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400K9-532AXSP04	275.1	426.5	326.7	366.6	-	275.5	424.9	326.6	365.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400K9-625AXSP04	313	475	368	410.6	-	313.5	473.4	367.7	409.7	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400K9-632AXSP04	299.2	457.7	352.9	394.9	754.6	299.4	456.7	352.7	394	749.8	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK400R3-425AXSP02	239.1	393	293.3	333.9	670.4	242.5	393.6	295.6	335.7	669.7	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK400R3-432AXSP04	249.4	390.5	298.1	335.4	-	249.9	389.6	297.5	335.1	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK400R3-525AXSP04	295.8	454.8	349.7	391.7	-	296.3	453.5	349.8	391.2	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK400R3-532AXSP04	278.7	431.6	331	371.4	-	279.3</													

EAW-FD1556ZK550C8-632AXSP04	341.6	525.9	404.8	453.1	-	342.9	525.5	405.1	453.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550C9-425AXSP02	271	445.3	332.7	379.2	763.5	275.1	446.3	335.6	381.3	762	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550C9-432AXSP02	249.1	413.3	307.2	350.7	712.6	253.2	414.8	309.9	352.7	712	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550C9-525AXSP02	299.5	488.2	366.2	415.6	828.1	304.7	490	369.6	418.5	828	761	12.4	(2) 4"	609	8.2	(2) 4"	913	14.8	(3) 4"
EAW-FD1556ZK550C9-532AXSP04	314.6	489	374.3	420.9	-	315.4	488.5	374.6	420.3	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550C9-625AXSP04	358.2	546.3	422.1	471.7	-	359.7	546.5	422.8	471.8	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550C9-632AXSP04	341.6	525.9	404.8	453.1	-	342.9	525.5	405.1	453.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K2-425AXSP02	259	425.7	317.9	362.1	728.1	263	427	320.4	364	727.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K2-432AXSP02	238.5	395.6	293.9	335.6	680.8	242.1	396.8	296.3	337.6	680	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K2-525AXSP04	320.3	493.6	379.6	425	-	321.2	492.7	379.6	424.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K2-532AXSP04	300.8	467.9	358.2	401.8	-	301.9	466.4	358.3	401.8	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K2-625AXSP04	343.6	523.1	404.8	452.1	-	344.2	522.1	404.5	451.1	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K2-632AXSP04	327.3	502.8	387.1	433.6	-	328.1	501.8	386.8	433.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K3-425AXSP02	259	425.7	317.9	362.1	728.1	263	427	320.4	364	727.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K3-432AXSP02	238.5	395.6	293.9	335.6	680.8	242.1	396.8	296.3	337.6	680	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K3-525AXSP04	320.3	493.6	379.6	425	-	321.2	492.7	379.6	424.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K3-532AXSP04	300.8	467.9	358.2	401.8	-	301.9	466.4	358.3	401.8	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K3-625AXSP04	343.6	523.1	404.8	452.1	-	344.2	522.1	404.5	451.1	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K3-632AXSP04	327.3	502.8	387.1	433.6	-	328.1	501.8	386.8	433.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K4-425AXSP02	259	425.7	317.9	362.1	728.1	263	427	320.4	364	727.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K4-432AXSP02	238.5	395.6	293.9	335.6	680.8	242.1	396.8	296.3	337.6	680	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K4-525AXSP04	320.3	493.6	379.6	425	-	321.2	492.7	379.6	424.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K4-532AXSP04	300.8	467.9	358.2	401.8	-	301.9	466.4	358.3	401.8	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K4-625AXSP04	343.6	523.1	404.8	452.1	-	344.2	522.1	404.5	451.1	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K4-632AXSP04	327.3	502.8	387.1	433.6	-	328.1	501.8	386.8	433.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K5-425AXSP02	259	425.7	317.9	362.1	728.1	263	427	320.4	364	727.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K5-432AXSP02	238.5	395.6	293.9	335.6	680.8	242.1	396.8	296.3	337.6	680	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K5-525AXSP04	320.3	493.6	379.6	425	-	321.2	492.7	379.6	424.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K5-532AXSP04	300.8	467.9	358.2	401.8	-	301.9	466.4	358.3	401.8	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K5-625AXSP04	343.6	523.1	404.8	452.1	-	344.2	522.1	404.5	451.1	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K5-632AXSP04	327.3	502.8	387.1	433.6	-	328.1	501.8	386.8	433.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K8-425AXSP02	259	425.7	317.9	362.1	728.1	263	427	320.4	364	727.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K8-432AXSP02	238.5	395.6	293.9	335.6	680.8	242.1	396.8	296.3	337.6	680	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K8-525AXSP04	320.3	493.6	379.6	425	-	321.2	492.7	379.6	424.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K8-532AXSP04	300.8	467.9	358.2	401.8	-	301.9	466.4	358.3	401.8	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K8-625AXSP04	343.6	523.1	404.8	452.1	-	344.2	522.1	404.5	451.1	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K8-632AXSP04	327.3	502.8	387.1	433.6	-	328.1	501.8	386.8	433.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K9-425AXSP02	259	425.7	317.9	362.1	728.1	263	427	320.4	364	727.2	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K9-432AXSP02	238.5	395.6	293.9	335.6	680.8	242.1	396.8	296.3	337.6	680	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550K9-525AXSP04	320.3	493.6	379.6	425	-	321.2	492.7	379.6	424.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K9-532AXSP04	300.8	467.9	358.2	401.8	-	301.9	466.4	358.3	401.8	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550K9-625AXSP04	343.6	523.1	404.8	452.1	-	344.2	522.1	404.5	451.1	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550K9-632AXSP04	327.3	502.8	387.1	433.6	-	328.1	501.8	386.8	433.3	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550R3-425AXSP02	264.3	433.9	324.6	369.6	744.3	268.3	435.7	327.1	371.8	742.8	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550R3-432AXSP02	243.4	403.7	300.2	342.5	696.3	247.3	405.1	302.8	344.8	694.5	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK550R3-525AXSP04	326.8	504	387.4	433.8	-	327.3	502.7	387.5	433.9	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550R3-532AXSP04	306.8	476.9	364.8	410.1	-	307.5	476.5	365.1	410.2	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK550R3-625AXSP04	350.4	533.9	412.9	461.3	-	351.2	533.1	412.8	460.5	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK550R3-632AXSP04	333.8	513.2	394.8	442.4	-	334.2	512.3	394.7	442.2	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK750C4-425AXSP04	317	496.1	378.3	425.9	-	318.1	495.9	378.9	426.3	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK750C4-432AXSP04	293.3	461.5	351	396.1	-	294.2	461.6	351.6	396.2	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK750C4-525AXSP04	348.1	537.9	413	462.9	-	349.2	538.1	413.7	463.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK750C4-532AXSP04	327.5	510.3	389.9	438	-	328.5	510.1	390.4	438.4	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK750C4-632AXSP04	354.5	546.7	420.3	471.4	-	356	546.6	421.4	471.8	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK750C5-425AXSP04	317	496.1	378.3	425.9	-	318.1	495.9	378.9	426.3	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK750C5-432AXSP04	293.3	461.5	351	396.1	-	294.2	461.6	351.6	396.2	-	304	20.2	4"	244	16.3	3"	365	28.4	4"
EAW-FD1556ZK750C5-525AXSP04	348.1	537.9	413	462.9	-	349.2	538.1	413.7	463.7	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK750C5-532AXSP04	327.5	510.3	389.9	438	-	328.5	510.1	390.4	438.4	-	378	21.4	4"	302	14.1	4"	453	26.4	(2) 4"
EAW-FD1556ZK750C5-632AXSP04	354.5	546.7	420.3	471.4	-	356	546.6	421.4	471.8	-	456	19.3	(2) 4"	365	15.1	4"	548	27	(2) 4"
EAW-FD1556ZK750K2-425AXSP02	274.8	451.2	337.5	384.4	774.3	279	453.6	340.5	387.3	773.6	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK750K2-432AXSP02	253.1	419.7	312.3	356.7	723.8	257.2	421.7	315	358.7	724	609	11.2	(2) 4"	487	7.4	(2) 4"	730	15.7	(2) 4"
EAW-FD1556ZK750K2-525AXSP02	303.5	494.4	370.6	421.4	838.9	308.4	496.2	374.1	423.7	838.9	761	12.4	(2) 4"	609	8.2	(2) 4"	913	14.8	(3) 4"
EAW-FD1556ZK750K2-532AXSP04	318.1	495.7	379.2	425.7	-														

EAW-FD91S1WK177F7-425AXSP16	23.8	37.6	28.6	32.3	62.7	23.8	37.3	28.5	32.1	62.1	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK177F7-432AXSP16	22	35	26.5	30	58.9	22	34.8	26.5	29.9	58.3	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK177F7-525AXSP16	25.9	40.5	30.9	34.7	66.8	25.9	40.2	30.8	34.6	66.2	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK177F7-532AXSP16	24.2	38.2	29.1	32.7	63.6	24.2	38	29	32.6	63.1	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK177F7-625AXSP16	28.4	43.7	33.6	37.7	71.4	28.4	43.4	33.5	37.5	70.6	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK177F7-632AXSP16	-	41.9	32.1	36	69.1	-	41.6	32	35.8	68.3	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK24716-425AXSP16	26.1	41.2	31.3	35.3	68.9	26.1	41	31.3	35.2	68.3	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK24716-432AXSP16	24	38.3	29	32.8	64.6	24.1	38.1	29	32.7	63.9	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK24716-525AXSP16	28.4	44.5	34	38.2	73.7	28.5	44.2	33.9	38.1	73	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK24716-532AXSP16	26.5	41.9	31.8	35.9	69.9	26.5	41.6	31.7	35.7	69.3	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK24716-625AXSP16	31.2	48.2	37.1	41.5	78.9	31.3	47.9	37	41.3	78.1	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK24716-632AXSP16	29.5	46.2	35.3	39.7	76.3	29.6	45.8	35.2	39.5	75.5	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK320P5-425AXSP16	28.3	44.9	34.1	38.5	75.2	28.4	44.5	34	38.3	74.4	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK320P5-432AXSP16	26	41.4	31.4	35.5	70	26.1	41.2	31.3	35.4	69.3	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK320P5-525AXSP16	31.1	48.8	37.3	41.9	81	31.1	48.5	37.1	41.7	80.3	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK320P5-532AXSP16	28.8	45.7	34.6	39.1	76.5	28.9	45.4	34.6	39	75.7	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK320P5-625AXSP16	34.5	53.4	41	46	87.7	34.5	53	40.8	45.7	86.7	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK320P5-632AXSP16	32.4	50.7	38.7	43.5	83.9	32.4	50.3	38.6	43.3	83.1	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK320P7-425AXSP16	29	45.7	34.8	39.3	76.8	29	45.5	34.7	39.1	76.1	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK320P7-432AXSP16	26.5	42.3	32.1	36.3	71.5	26.6	42.1	32	36.1	70.9	56	18.4	1-1/2"	45	12.1	1-1/2"	68	25.9	1-1/2"
EAW-FD91S1WK320P7-525AXSP16	31.7	49.8	38	42.8	82.8	31.8	49.5	37.9	42.6	82.1	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK320P7-532AXSP16	29.4	46.6	35.4	39.9	78	29.5	46.3	35.3	39.8	77.3	68	19.8	1-1/2"	54	13.1	1-1/2"	81	23.6	2"
EAW-FD91S1WK320P7-625AXSP16	35.2	54.6	41.8	47	89.6	35.2	54.1	41.7	46.7	88.6	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S1WK320P7-632AXSP16	33.1	51.7	39.5	44.4	85.7	33.1	51.4	39.4	44.2	84.9	84	17.7	2"	68	14.7	1-1/2"	101	24.9	2"
EAW-FD91S2WK177F7-425AXSP12	49.2	75.6	58.2	65.1	-	49	74.9	57.8	64.6	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK177F7-432AXSP12	45.4	70.4	54	60.5	117.3	45.2	69.8	53.6	60.1	116	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK177F7-525AXSP12	54.2	82.5	63.9	71.3	134.9	54	81.8	63.4	70.8	133.5	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK177F7-532AXSP12	50.8	78	60.1	67.3	128.6	50.5	77.3	59.7	66.7	127.1	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK177F7-625AXSP16	60.7	90.2	70.6	78.3	-	60.2	89.2	69.9	77.5	-	84	29.1	2"	68	22.3	1-1/2"	101	40.9	2"
EAW-FD91S2WK177F7-632AXSP16	57.6	86.6	67.4	75	140.3	57.3	85.6	66.8	74.2	138.6	84	29.1	2"	68	22.3	1-1/2"	101	40.9	2"
EAW-FD91S2WK24716-425AXSP12	53.6	82.7	63.6	71.3	-	53.4	82.2	63.2	70.8	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK24716-432AXSP12	49.5	76.9	58.9	66.1	-	49.3	76.3	58.6	65.7	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK24716-525AXSP12	59.4	90.7	70.1	78.3	148.8	59.3	89.9	69.7	77.7	147.3	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK24716-532AXSP12	55.5	85.5	65.8	73.6	141.4	55.3	84.7	65.3	73.1	139.9	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK24716-625AXSP12	65.3	98.4	76.5	85.2	159.3	65	97.4	76.1	84.5	157.6	113	24.5	2"	90	16.1	2"	135	29.1	3"
EAW-FD91S2WK24716-632AXSP16	63.2	95.2	74	82.4	-	62.8	94.4	73.4	81.7	-	84	29.1	2"	68	22.3	1-1/2"	101	40.9	2"
EAW-FD91S2WK320P5-425AXSP12	58.1	90.1	69	77.6	-	57.9	89.4	68.7	77	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK320P5-432AXSP12	53.5	83.1	63.7	71.5	-	53.2	82.6	63.3	71.1	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK320P5-525AXSP12	65	99.5	76.8	85.7	-	64.6	98.6	76.2	85.2	-	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK320P5-625AXSP12	60.3	93.1	71.5	80.2	-	60.1	92.4	71	79.6	-	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK320P5-632AXSP12	72.1	108.9	84.6	94.2	177	71.7	107.8	83.9	93.4	174.9	113	24.5	2"	90	16.1	2"	135	29.1	3"
EAW-FD91S2WK320P7-425AXSP12	67.7	103.4	79.9	89.3	169.5	67.4	102.4	79.4	88.5	167.6	113	24.5	2"	90	16.1	2"	135	29.1	3"
EAW-FD91S2WK320P7-432AXSP12	59.3	91.9	70.5	79.1	-	59.2	91.3	70.1	78.6	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK320P7-432AXSP12	54.4	85	64.9	72.9	-	54.2	84.3	64.5	72.5	-	73	21.9	2"	59	16.7	1-1/2"	88	30.7	2"
EAW-FD91S2WK320P7-525AXSP12	66.3	101.6	78.3	87.7	-	66	100.7	77.8	87	-	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK320P7-532AXSP12	61.6	95.1	73	81.8	-	61.3	94.2	72.5	81.5	-	90	22.9	2"	72	15.1	2"	108	32.1	2"
EAW-FD91S2WK320P7-625AXSP12	73.5	111.1	86.3	96.2	180.8	73.2	110.1	85.7	95.4	178.7	113	24.5	2"	90	16.1	2"	135	29.1	3"
EAW-FD91S2WK320P7-632AXSP12	69.2	105.6	81.6	91.2	173.2	68.9	104.6	81.1	90.4	171.3	113	24.5	2"	90	16.1	2"	135	29.1	3"
EAW-FD91S3WK177F7-425AXSP08	74.6	114.7	88.2	98.9	-	74.3	113.7	87.7	98.1	187.4	113	23.6	2"	90	15.5	2"	135	27.8	3"
EAW-FD91S3WK177F7-432AXSP08	68.9	106.8	82	92.1	178	68.7	106	81.4	91.4	176.1	113	23.6	2"	90	15.5	2"	135	27.8	3"
EAW-FD91S3WK177F7-525AXSP08	82.8	125.9	97.5	108.8	205.6	82.5	124.7	96.8	107.9	203.1	141	20.4	3"	113	17.2	2"	169	28.6	3"
EAW-FD91S3WK177F7-532AXSP08	77.7	119.2	91.9	102.9	196.2	77.3	118.1	91.4	102	194.1	141	20.4	3"	113	17.2	2"	169	28.6	3"
EAW-FD91S3WK177F7-625AXSP08	88.8	133.7	104.1	115.9	215.6	88.4	132.4	103.2	114.8	213.1	169	21	3"	135	13.8	3"	203	29.4	3"
EAW-FD91S3WK177F7-632AXSP08	84.3	128.3	99.4	110.9	208.8	83.9	127	98.5	109.9	206.5	169	21	3"	135	13.8	3"	203	29.4	3"
EAW-FD91S3WK24716-425AXSP08	81.5	125.6	96.5	108.3	-	81.2	124.6	96	107.5	-	113	23.6	2"	90	15.5	2"	135	27.8	3"
EAW-FD91S3WK24716-432AXSP08	75.2	116.9	89.5	100.6	-	75.1	116	88.9	99.9	-	113	23.6	2"	90	15.5	2"	135	27.8	3"
EAW-FD91S3WK24716-525AXSP08	90.9	138.5	107.1	119.6	226.8	90.6	137.2	106.5	118.7	224.5	141	20.4	3"	113	17.2	2"	169	28.6	3"
EAW-FD91S3WK24716-532AXSP08	85.1	130.8	100.8	112.7	215.8	84.7	129.7	100	111.8	213.6	141	20.4	3"	113	17.2	2"	169	28.6	3"
EAW-FD91S3WK24716-625AXSP08	97.8	147.3	114.6	127.5	238.4	97.3	146	113.8	126.6	235.8	169	21	3"	135	13.8	3"	203	29.4	3"
EAW-FD91S3WK24716-632AXSP08	92.5	141	109.1	121.8	230.4	92.2	139.7	108.4	120.9	227.8	169	21	3"	135	13.8	3"	203	29.4	3"
EAW-FD91S3WK320P5-425AXSP08	88.5	136.7	105	117.7	-	88.1	135.7	104.3	116.9	-	113	23.6	2"	90	15.5	2"	135	27.8	3"
EAW-FD91S3WK320P5-432AXSP08	81.3	126.4	96.8	108.7	-	80.9	125.4	96.2	108	-	113	23.6	2"	90	15.5	2"	135	27.8	3"
EAW-FD91S3WK320P5-525AXSP08	99.4	151.9	117.4	131.1	-	99	150.5	116.4	130.2	-	141	20.4	3"	113	17.2	2"	169	28.6	3"
EAW-FD91S3WK320P5-532AXSP08	92.5	142.5	109.6	122.7	-	92.1	141.2	108.8	121.8	233.5	141	20.4	3"	113	17.2	2"	169	28.6	3"
EAW-FD91S3WK320P5-625AXSP08	107.9	163	126.6	141.1	264.9	107.2	161.4	125.5	139.9	261.7	169	21	3"	135	13.8	3"	203		

EAW-FD915SWK177F7-632AXSP06	142.7	214.9	167	186	348.8	141.6	212.5	165.6	184.4	344.5	225	26.3	3"	180	17.4	3"	270	33.6	4"
EAW-FD915SWK24716-425AXSP04	132.4	205.9	157.9	177.3	342.9	132	204.6	157.2	176.1	340	225	18.7	3"	180	12.3	3"	270	22.9	4"
EAW-FD915SWK24716-432AXSP04	121.9	191.4	146.2	164.4	320.8	121.7	190.2	145.6	163.7	318.2	225	18.7	3"	180	12.3	3"	270	22.9	4"
EAW-FD915SWK24716-525AXSP06	152.4	231.1	179	199.7	-	151.7	229	177.7	198.2	-	186	25.2	3"	149	16.6	3"	223	35.4	3"
EAW-FD915SWK24716-532AXSP06	142.7	218	168.2	188.1	-	141.9	216.1	167	186.7	-	186	25.2	3"	149	16.6	3"	223	35.4	3"
EAW-FD915SWK24716-625AXSP06	164.9	246.9	192.6	213.9	-	164	244.5	190.9	212	-	225	26.3	3"	180	17.4	3"	270	33.6	4"
EAW-FD915SWK24716-632AXSP06	156.4	236.2	183.4	204.4	-	155.6	234.1	182	202.8	-	225	26.3	3"	180	17.4	3"	270	33.6	4"
EAW-FD915SWK320P5-425AXSP04	143.8	224.3	171.4	192.7	374.5	143.6	222.4	170.6	191.7	370.6	225	18.7	3"	180	12.3	3"	270	22.9	4"
EAW-FD915SWK320P5-432AXSP04	131.8	207.2	158	177.9	347.9	131.5	205.5	157	176.8	344.9	225	18.7	3"	180	12.3	3"	270	22.9	4"
EAW-FD915SWK320P5-525AXSP04	161.7	249.4	191.9	217	411.5	161.1	247.4	191	213.6	407.1	282	17	4"	225	13.6	3"	338	23.9	4"
EAW-FD915SWK320P5-532AXSP04	150	233.7	178.9	201	388.7	149.7	231.9	178.2	199.8	384.5	282	17	4"	225	13.6	3"	338	23.9	4"
EAW-FD915SWK320P5-625AXSP06	181.8	273.3	212.7	236.7	-	180.6	270.3	210.9	234.4	-	225	26.3	3"	180	17.4	3"	270	33.6	4"
EAW-FD915SWK320P5-632AXSP06	171.1	259.2	201	224.2	-	170.1	256.6	199.3	222.3	-	225	26.3	3"	180	17.4	3"	270	33.6	4"
EAW-FD915SWK320P7-425AXSP04	146.7	228.7	175	196.7	-	146.6	227.2	174.2	195.4	-	225	18.7	3"	180	12.3	3"	270	22.9	4"
EAW-FD915SWK320P7-432AXSP04	134.4	211.3	161.3	181.3	355.7	134.3	210.1	160.4	180.6	352.3	225	18.7	3"	180	12.3	3"	270	22.9	4"
EAW-FD915SWK320P7-525AXSP04	165	254.7	195.8	219.5	420.5	164.5	252.8	195	218.2	416.2	282	17	4"	225	13.6	3"	338	23.9	4"
EAW-FD915SWK320P7-532AXSP04	153.1	238.4	182.9	205.3	397.3	152.8	236.7	181.9	204.1	393.2	282	17	4"	225	13.6	3"	338	23.9	4"
EAW-FD915SWK320P7-625AXSP04	178.7	273.2	211.3	236	446.8	178.3	271.1	209.9	234.5	441.7	338	17.8	4"	270	17.7	4"	406	25	4"
EAW-FD915SWK320P7-632AXSP06	174.6	264.7	205.1	228.9	-	173.4	262.2	203.5	227.1	-	225	26.3	3"	180	17.4	3"	270	33.6	4"
EAW-FD915GWK177F7-425AXSP04	147.8	227.4	175.1	196.2	376.3	147.1	225.7	173.8	194.8	372.3	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK177F7-432AXSP04	136.6	211.9	162.6	182.6	353.3	135.9	210.1	161.5	181.2	349.6	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK177F7-525AXSP04	164.4	250.2	193.6	216.2	408.7	163.5	247.8	192.4	214.4	403.9	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK177F7-532AXSP04	154	236.8	182.5	204.2	389.9	153.5	234.6	181.1	202.6	385.7	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK177F7-625AXSP04	176.5	265.8	206.9	230.4	429.3	175.6	263.2	205.2	228.4	424.3	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK177F7-632AXSP04	167.5	254.7	197.1	220.2	415.6	166.5	252.5	195.8	218.4	410.5	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK24716-425AXSP04	161.4	249.3	191.4	214.8	-	160.8	247.3	190.5	213.3	-	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK24716-432AXSP04	149.1	231.5	177.3	199.4	-	148.5	229.8	176.3	197.8	-	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK24716-525AXSP04	180.5	275.1	212.7	237.6	450.8	179.6	272.7	211.1	235.8	446.3	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK24716-532AXSP04	168.5	259.4	199.6	223.6	428.8	167.8	257.5	198.5	222	424.4	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK24716-625AXSP04	194	292.7	227.8	253.5	474.7	193	290.2	226.1	251.6	469.5	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK24716-632AXSP04	183.7	280.2	216.7	242	458.1	182.8	277.7	215.3	240.1	453.4	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK320P5-425AXSP04	175.4	271.2	208.2	233.5	-	174.4	268.9	206.8	231.9	-	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK320P5-432AXSP04	161	250.7	191.7	215.4	-	160.3	248.7	190.5	214	-	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK320P5-525AXSP04	197.3	301.8	232.7	260.3	-	196.3	299	231.2	258.5	-	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK320P5-532AXSP04	183.4	282.5	217.5	243.6	468.3	182.6	280.4	215.9	241.7	463.3	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK320P5-625AXSP04	214	323.9	251.4	280	527.3	213	320.8	249.4	278	521	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK320P5-632AXSP04	201.1	307.3	237.4	265.3	504.1	200	304.3	235.7	263.1	498.5	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK320P7-425AXSP04	178.6	277.1	212.2	238.5	-	178.1	274.8	211.1	236.8	-	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK320P7-432AXSP04	164	255.8	195.7	220	-	163.7	253.8	194.6	218.3	-	225	21.6	3"	180	14.2	3"	270	26.9	4"
EAW-FD915GWK320P7-525AXSP04	201.4	308.2	237.5	265.7	-	200.4	305.5	236.1	263.7	-	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK320P7-532AXSP04	187.2	288.6	221.7	248.7	-	186.5	286.1	220.4	246.9	-	282	19.8	4"	225	15.5	3"	338	27.9	4"
EAW-FD915GWK320P7-625AXSP04	218.4	330.4	256.3	285.9	538.1	217.2	327.3	254.7	283.6	532.5	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-FD915GWK320P7-632AXSP04	205.2	313.8	242.2	270.8	515.6	204.2	310.9	240.7	268.7	509.5	338	20.6	4"	270	13.6	4"	406	29	4"
EAW-HD403SQV037M4-525AXSP02	1125.5	1815.9	1368.1	1550.5	3063.7	1136.6	1812.8	1371.4	1550.6	3043.2	3156	12.4	6"	2525	8.1	6"	3787	17.4	6"
EAW-HD403SQV037M4-625AXSP02	-	1941.3	1470.1	1661.1	3248.8	-	1937.8	1475	1663.3	3225	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV037M4-632AXSP02	-	1843.8	1387.5	1573.8	3113.6	-	1840	1392.5	1573.3	3092.1	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV037M4-525AXSP02	1088.8	1756.5	1325	1500.9	2964.4	1101.1	1753.3	1327.9	1500.8	2944.4	3156	12.4	6"	2525	8.1	6"	3787	17.4	6"
EAW-HD403SQV037M4-625AXSP02	-	1877.7	1421.5	1605.6	3135.5	-	1874.1	1426.1	1607.4	3116.2	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV037M4-632AXSP02	-	1784	1344.1	1523.8	3013.5	-	1780.1	1348.7	1523.2	2988.6	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV045M4-525AXSP02	1177.3	1901.8	1432.4	1622	3209.4	1187.5	1899.1	1436.4	1622.7	3188.7	3156	12.4	6"	2525	8.1	6"	3787	17.4	6"
EAW-HD403SQV045M4-625AXSP02	1274.4	2039.3	1542	1743.5	3412.9	1287.5	2035.8	1547.4	1745.8	3391.9	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV045M4-632AXSP02	-	1930.2	1452	1648.2	3260.3	-	1926.9	1457.9	1648.4	3238.6	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV045M4-525AXSP02	1139.5	1840	1385.5	1570.6	3101.5	1151.1	1837.2	1389.1	1571	3081.3	3156	12.4	6"	2525	8.1	6"	3787	17.4	6"
EAW-HD403SQV045M4-625AXSP02	-	1967.3	1489.1	1682.9	3293.6	-	1964.1	1494.4	1685.4	3269.8	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV045M4-632AXSP02	-	1868	1407.2	1593.9	3155.8	-	1864.5	1410.3	1593.8	3134.5	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV055M4-525AXSP02	1255.3	2033.2	1529.5	1734	3434.8	1269.9	2032	1535.2	1736.2	3414.9	3156	12.4	6"	2525	8.1	6"	3787	17.4	6"
EAW-HD403SQV055M4-625AXSP02	1361.3	2182.6	1648.9	1866	3654.9	1374.8	2180.9	1656.4	1867.8	3635.5	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV055M4-632AXSP02	1275	2061.9	1551.9	1760.7	3491.4	1289.1	2060.1	1557.1	1762.4	3470.4	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV055M4-525AXSP02	1203.2	1946.3	1464.6	1659.1	3282.5	1214.5	1941.8	1469.6	1660.8	3263.1	3156	12.4	6"	2525	8.1	6"	3787	17.4	6"
EAW-HD403SQV055M4-625AXSP02	1301.4	2081.6	1575.1	1781.4	3485.8	1313.9	2079.7	1579.6	1782.7	3467.1	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-HD403SQV055M4-632AXSP02	-	1974.5	1486.6	1685.3	3337.8	-	1972.3	1491.1	1686.4	3317.3	3787	13.7	6"	3030	9	6"	4544	14.7	(2) 6"
EAW-VD15S1PB8370C2-425AXSP16	51.6	82.3	62.4	70.5	138.7	52	82.1	62.4	70.5	137.8	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB8370C2-432AXSP16	47.6	76.7	57.8	65.6															

EAW-VD15S1PB370K5-625AXSP16	58.6	91.6	70	78.7	150.7	58.9	91.2	70.1	78.6	149.7	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB370K5-632AXSP16	-	88.1	66.9	75.4	146.4	-	87.7	67.1	75.4	145.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB370K8-425AXSP16	49.7	79.3	60	67.9	133.3	49.9	79	60.1	67.7	132.4	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB370K8-432AXSP16	45.9	74	55.7	63.1	125.2	46.2	73.8	55.7	63.1	124.5	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB370K8-525AXSP16	53.7	84.9	64.6	72.8	141.4	54	84.7	64.6	72.7	140.5	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB370K8-532AXSP16	50.3	80.3	60.8	68.7	135	50.7	80.1	60.9	68.7	134.3	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB370K8-625AXSP16	58.6	91.6	70	78.7	150.7	58.9	91.2	70.1	78.6	149.7	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB370K8-632AXSP16	-	88.1	66.9	75.4	146.4	-	87.7	67.1	75.4	145.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400B3-425AXSP16	50.1	80	60.6	68.5	134.5	50.4	79.8	60.7	68.4	133.9	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400B3-432AXSP16	46.4	74.8	56.3	63.8	126.7	46.7	74.7	56.5	63.8	126	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400B3-525AXSP16	54	85.5	64.9	73.3	142.5	54.4	85.3	65.1	73.2	141.7	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400B3-532AXSP16	50.7	81.1	61.3	69.4	136.3	51.1	80.9	61.5	69.3	135.4	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400B3-625AXSP16	58.8	91.7	70.2	78.8	151.1	59.2	91.5	70.3	78.9	150.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400B3-632AXSP16	-	88.5	67.4	75.9	147.4	56.5	88.4	67.5	75.9	146.5	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400C3-425AXSP16	51.6	82.3	62.4	70.5	138.7	52	82.1	62.4	70.5	137.8	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400C3-432AXSP16	47.6	76.7	57.8	65.6	130	47.9	76.5	57.9	65.5	129.3	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400C3-525AXSP16	55.9	88.4	67.2	75.7	147.4	56.2	88.1	67.3	75.7	146.5	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400C3-532AXSP16	52.2	83.5	63.2	71.4	140.6	52.6	83.4	63.2	71.4	139.6	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400C3-625AXSP16	60.9	95.2	72.9	81.9	157	61.3	95	73	81.8	156.1	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400C3-632AXSP16	58	91.7	69.7	78.6	152.5	58.4	91.3	69.8	78.5	151.5	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400C9-425AXSP16	51.6	82.3	62.4	70.5	138.7	52	82.1	62.4	70.5	137.8	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400C9-432AXSP16	47.6	76.7	57.8	65.6	130	47.9	76.5	57.9	65.5	129.3	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400C9-525AXSP16	55.9	88.4	67.2	75.7	147.4	56.2	88.1	67.3	75.7	146.5	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400C9-532AXSP16	52.2	83.5	63.2	71.4	140.6	52.6	83.4	63.2	71.4	139.6	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400C9-625AXSP16	60.9	95.2	72.9	81.9	157	61.3	95	73	81.8	156.1	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400C9-632AXSP16	58	91.7	69.7	78.6	152.5	58.4	91.3	69.8	78.5	151.5	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400K3-425AXSP16	49.7	79.3	60	67.9	133.3	49.9	79	60.1	67.7	132.4	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400K3-432AXSP16	45.9	74	55.7	63.1	125.2	46.2	73.8	55.7	63.1	124.5	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400K3-525AXSP16	53.7	84.9	64.6	72.8	141.4	54	84.7	64.6	72.7	140.5	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400K3-532AXSP16	50.3	80.3	60.8	68.7	135	50.7	80.1	60.9	68.7	134.3	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400K3-625AXSP16	58.6	91.6	70	78.7	150.7	58.9	91.2	70.1	78.6	149.7	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400K3-632AXSP16	-	88.1	66.9	75.4	146.4	-	87.7	67.1	75.4	145.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400K9-425AXSP16	49.7	79.3	60	67.9	133.3	49.9	79	60.1	67.7	132.4	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400K9-432AXSP16	45.9	74	55.7	63.1	125.2	46.2	73.8	55.7	63.1	124.5	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400K9-525AXSP16	53.7	84.9	64.6	72.8	141.4	54	84.7	64.6	72.7	140.5	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400K9-532AXSP16	50.3	80.3	60.8	68.7	135	50.7	80.1	60.9	68.7	134.3	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400K9-625AXSP16	58.6	91.6	70	78.7	150.7	58.9	91.2	70.1	78.6	149.7	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400K9-632AXSP16	-	88.1	66.9	75.4	146.4	-	87.7	67.1	75.4	145.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400R3-425AXSP16	50.5	80.6	61	69	135.6	50.8	80.4	61.1	68.9	134.9	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400R3-432AXSP16	46.7	75.3	56.6	64.2	127.6	47	75.1	56.8	64.2	126.8	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB400R3-525AXSP16	54.6	86.3	65.6	73.9	144	54.9	86.2	65.7	73.9	143.1	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400R3-532AXSP16	51.2	81.6	61.7	69.9	137.4	51.5	81.5	61.9	69.9	136.5	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB400R3-625AXSP16	59.6	93	71.1	79.9	153.3	59.9	92.8	71.2	79.8	152.2	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB400R3-632AXSP16	56.7	89.5	68.1	76.7	149	57.1	89.3	68.2	76.7	148	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550B3-425AXSP16	54.8	87.5	66.2	75	147.5	55.1	87.4	66.4	75	146.8	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB550B3-432AXSP16	50.6	81.6	61.5	69.7	138.6	51	81.5	61.6	69.8	137.9	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB550B3-525AXSP16	59	93.6	71.1	80.2	156.3	59.5	93.5	71.2	80.3	155.7	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB550B3-532AXSP16	55.4	88.7	67	75.7	149.2	55.7	88.6	67.1	75.7	148.4	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB550B3-625AXSP16	64.3	100.7	76.9	86.5	166.2	64.8	100.6	77.1	86.6	165.4	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550B3-632AXSP16	61.3	97.1	73.8	83.2	161.8	61.8	96.9	73.9	83.2	161	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550C2-425AXSP16	57.7	92.1	69.8	79	155.7	58	92	70	78.8	154.9	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB550C2-432AXSP16	53	85.4	64.4	73.1	145.5	53.4	85.3	64.6	73	144.6	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB550C2-525AXSP16	62.7	99.4	75.5	85.2	166.3	63.1	99.1	75.6	85.2	165.4	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB550C2-532AXSP16	58.4	93.5	70.6	80	157.6	58.7	93.3	70.8	80	156.7	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB550C2-625AXSP16	68.7	107.8	82.3	92.6	178.2	69.2	107.6	82.4	92.5	177.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550C2-632AXSP16	65.1	103.2	78.4	88.3	172	65.6	102.9	78.4	88.4	171.1	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550C3-425AXSP16	57.7	92.1	69.8	79	155.7	58	92	70	78.8	154.9	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB550C3-432AXSP16	53	85.4	64.4	73.1	145.5	53.4	85.3	64.6	73	144.6	113	17.3	1-1/2"	90	11.4	1-1/2"	135	24.3	1-1/2"
EAW-VD15S1PB550C3-525AXSP16	62.7	99.4	75.5	85.2	166.3	63.1	99.1	75.6	85.2	165.4	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB550C3-532AXSP16	58.4	93.5	70.6	80	157.6	58.7	93.3	70.8	80	156.7	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB550C3-625AXSP16	68.7	107.8	82.3	92.6	178.2	69.2	107.6	82.4	92.5	177.3	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550C3-632AXSP16	65.1	103.2	78.4	88.3	172	65.6	102.9	78.4	88.4	171.1	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB550C4-425AXSP16	53	85.4	64.4	73.1	145.5	53.4	85.3	64.6	73	144.6	113	17.3	1-1/2"	90	11.4	1-1/2			



EAW-VD15S1PB750R3-525AXSP16	62.4	99.1	75.3	84.9	165.9	62.9	99	75.5	85	165.2	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB750R3-532AXSP16	58.4	93.6	70.7	79.9	157.8	58.9	93.5	70.8	80	157.1	135	18.7	1-1/2"	108	12.3	1-1/2"	162	22	2"
EAW-VD15S1PB750R3-625AXSP16	68.3	107.1	81.7	91.9	177.1	68.9	107	82	92	176.2	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PB750R3-632AXSP16	64.9	102.8	78	88.1	171.5	65.4	102.7	78.3	88.1	170.7	169	16.6	2"	135	14	1-1/2"	203	23.3	2"
EAW-VD15S1PI370C2-425AXSP16	61.4	95.6	73.3	82.3	158.8	61.3	94.9	72.9	81.7	157.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C2-432AXSP16	56.7	89.1	68	76.5	149.1	56.6	88.5	67.6	76.1	147.6	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C2-525AXSP16	66.8	103	79.2	88.9	169.4	66.6	102.2	78.9	88.3	167.8	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C2-532AXSP16	62.4	97.3	74.5	83.6	161.4	62.3	96.6	74.1	83.2	159.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C2-625AXSP16	73.1	111.6	86.2	96.3	181	73	110.6	85.8	95.7	179	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C2-632AXSP16	69.4	106.9	82.3	92.1	175.2	69.3	106.1	81.9	91.5	173.4	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C4-425AXSP16	61.4	95.6	73.3	82.3	158.8	61.3	94.9	72.9	81.7	157.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C4-432AXSP16	56.7	89.1	68	76.5	149.1	56.6	88.5	67.6	76.1	147.6	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C4-525AXSP16	66.8	103	79.2	88.9	169.4	66.6	102.2	78.9	88.3	167.8	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C4-532AXSP16	62.4	97.3	74.5	83.6	161.4	62.3	96.6	74.1	83.2	159.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C4-625AXSP16	73.1	111.6	86.2	96.3	181	73	110.6	85.8	95.7	179	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C4-632AXSP16	69.4	106.9	82.3	92.1	175.2	69.3	106.1	81.9	91.5	173.4	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C5-425AXSP16	61.4	95.6	73.3	82.3	158.8	61.3	94.9	72.9	81.7	157.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C5-432AXSP16	56.7	89.1	68	76.5	149.1	56.6	88.5	67.6	76.1	147.6	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C5-525AXSP16	66.8	103	79.2	88.9	169.4	66.6	102.2	78.9	88.3	167.8	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C5-532AXSP16	62.4	97.3	74.5	83.6	161.4	62.3	96.6	74.1	83.2	159.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C5-625AXSP16	73.1	111.6	86.2	96.3	181	73	110.6	85.8	95.7	179	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C5-632AXSP16	69.4	106.9	82.3	92.1	175.2	69.3	106.1	81.9	91.5	173.4	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C8-425AXSP16	61.4	95.6	73.3	82.3	158.8	61.3	94.9	72.9	81.7	157.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C8-432AXSP16	56.7	89.1	68	76.5	149.1	56.6	88.5	67.6	76.1	147.6	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370C8-525AXSP16	66.8	103	79.2	88.9	169.4	66.6	102.2	78.9	88.3	167.8	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C8-532AXSP16	62.4	97.3	74.5	83.6	161.4	62.3	96.6	74.1	83.2	159.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370C8-625AXSP16	73.1	111.6	86.2	96.3	181	73	110.6	85.8	95.7	179	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370C8-632AXSP16	69.4	106.9	82.3	92.1	175.2	69.3	106.1	81.9	91.5	173.4	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K2-425AXSP16	59.1	91.9	70.5	79.2	152.7	59	91.3	70.2	78.7	151.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K2-432AXSP16	54.7	85.9	65.6	73.9	143.7	54.6	85.4	65.3	73.4	142.3	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K2-525AXSP16	64.1	98.9	76.1	85.2	162.3	64	98.2	75.7	84.7	160.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K2-532AXSP16	60	93.5	71.6	80.4	154.9	60	92.8	71.3	80	153.3	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K2-625AXSP16	70.1	106.7	82.6	92.1	173	69.9	105.9	82.1	91.5	171.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K2-632AXSP16	66.6	102.5	78.9	88.4	167.9	66.6	101.7	78.5	87.8	166	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K4-425AXSP16	59.1	91.9	70.5	79.2	152.7	59	91.3	70.2	78.7	151.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K4-432AXSP16	54.7	85.9	65.6	73.9	143.7	54.6	85.4	65.3	73.4	142.3	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K4-525AXSP16	64.1	98.9	76.1	85.2	162.3	64	98.2	75.7	84.7	160.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K4-532AXSP16	60	93.5	71.6	80.4	154.9	60	92.8	71.3	80	153.3	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K4-625AXSP16	70.1	106.7	82.6	92.1	173	69.9	105.9	82.1	91.5	171.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K4-632AXSP16	66.6	102.5	78.9	88.4	167.9	66.6	101.7	78.5	87.8	166	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K5-425AXSP16	59.1	91.9	70.5	79.2	152.7	59	91.3	70.2	78.7	151.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K5-432AXSP16	54.7	85.9	65.6	73.9	143.7	54.6	85.4	65.3	73.4	142.3	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K5-525AXSP16	64.1	98.9	76.1	85.2	162.3	64	98.2	75.7	84.7	160.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K5-532AXSP16	60	93.5	71.6	80.4	154.9	60	92.8	71.3	80	153.3	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K5-625AXSP16	70.1	106.7	82.6	92.1	173	69.9	105.9	82.1	91.5	171.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K5-632AXSP16	66.6	102.5	78.9	88.4	167.9	66.6	101.7	78.5	87.8	166	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K8-425AXSP16	59.1	91.9	70.5	79.2	152.7	59	91.3	70.2	78.7	151.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K8-432AXSP16	54.7	85.9	65.6	73.9	143.7	54.6	85.4	65.3	73.4	142.3	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI370K8-525AXSP16	64.1	98.9	76.1	85.2	162.3	64	98.2	75.7	84.7	160.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K8-532AXSP16	60	93.5	71.6	80.4	154.9	60	92.8	71.3	80	153.3	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI370K8-625AXSP16	70.1	106.7	82.6	92.1	173	69.9	105.9	82.1	91.5	171.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI370K8-632AXSP16	66.6	102.5	78.9	88.4	167.9	66.6	101.7	78.5	87.8	166	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI400B3-425AXSP16	59.9	93.2	71.5	80.3	154.7	59.8	92.6	71.1	79.7	153.4	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI400B3-432AXSP16	55.4	87.1	66.5	74.9	145.5	55.4	86.5	66.2	74.4	144.4	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI400B3-525AXSP16	65	100.2	77.1	86.3	164.6	64.8	99.4	76.8	85.9	163	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI400B3-532AXSP16	60.8	94.8	72.5	81.5	157.1	60.8	94.2	72.3	81.1	155.6	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI400B3-625AXSP16	70.9	108	83.5	92.2	175.1	70.8	107.1	83.2	92.7	173.3	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI400B3-632AXSP16	67.5	103.9	80	89.6	170.2	67.5	103.1	79.6	89	168.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PI400C3-425AXSP16	61.4	95.6	73.3	82.3	158.8	61.3	94.9	72.9	81.7	157.2	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI400C3-432AXSP16	56.7	89.1	68	76.5	149.1	56.6	88.5	67.6	76.1	147.6	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1PI400C3-525AXSP16	66.8	103	79.2	88.9	169.4	66.6	102.2	78.9	88.3	167.8	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI400C3-532AXSP16	62.4	97.3	74.5	83.6	161.4	62.3	96.6	74.1	83.2	159.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1PI400C3-625AXSP16	73.																		



Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1P1750C9-425AXSP16	74	115.4	88.2	99.1	-	73.9	114.7	87.9	98.8	-	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750C9-432AXSP16	68	107.1	81.5	91.9	180.1	68	106.5	81.4	91.5	178.7	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750C9-525AXSP16	80.6	124.7	95.8	107.5	206.5	80.6	124.1	95.5	106.9	204.9	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750C9-532AXSP16	75	117.2	89.7	100.8	195.8	75	116.6	89.4	100.4	194.2	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750C9-625AXSP16	88.7	135.7	104.9	117.3	221.8	88.6	134.9	104.5	116.7	220.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750C9-632AXSP16	83.8	129.8	99.6	111.8	213.9	83.9	128.9	99.3	111.3	212.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K2-425AXSP16	71.5	111.6	85.3	95.9	186.3	71.5	110.9	85.1	95.4	184.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K2-432AXSP16	65.9	103.6	79	89	174.4	65.9	103.1	78.9	88.6	173	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K2-525AXSP16	77.8	120.3	92.6	103.6	199.1	77.8	119.7	92.2	103.2	197.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K2-532AXSP16	72.5	113.3	86.8	97.5	189.1	72.5	112.7	86.4	97	187.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K2-625AXSP16	85.4	130.6	100.9	112.8	213.3	85.4	129.7	100.6	112.3	211.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K2-632AXSP16	80.9	125	96.1	107.9	206.2	80.9	124.3	95.9	107.3	204.2	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K3-425AXSP16	71.5	111.6	85.3	95.9	186.3	71.5	110.9	85.1	95.4	184.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K3-432AXSP16	65.9	103.6	79	89	174.4	65.9	103.1	78.9	88.6	173	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K3-525AXSP16	77.8	120.3	92.6	103.6	199.1	77.8	119.7	92.2	103.2	197.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K3-532AXSP16	72.5	113.3	86.8	97.5	189.1	72.5	112.7	86.4	97	187.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K3-625AXSP16	85.4	130.6	100.9	112.8	213.3	85.4	129.7	100.6	112.3	211.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K3-632AXSP16	80.9	125	96.1	107.9	206.2	80.9	124.3	95.9	107.3	204.2	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K4-425AXSP16	71.5	111.6	85.3	95.9	186.3	71.5	110.9	85.1	95.4	184.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K4-432AXSP16	65.9	103.6	79	89	174.4	65.9	103.1	78.9	88.6	173	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K4-525AXSP16	77.8	120.3	92.6	103.6	199.1	77.8	119.7	92.2	103.2	197.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K4-532AXSP16	72.5	113.3	86.8	97.5	189.1	72.5	112.7	86.4	97	187.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K4-625AXSP16	85.4	130.6	100.9	112.8	213.3	85.4	129.7	100.6	112.3	211.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K4-632AXSP16	80.9	125	96.1	107.9	206.2	80.9	124.3	95.9	107.3	204.2	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K5-425AXSP16	71.5	111.6	85.3	95.9	186.3	71.5	110.9	85.1	95.4	184.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K5-432AXSP16	65.9	103.6	79	89	174.4	65.9	103.1	78.9	88.6	173	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K5-525AXSP16	77.8	120.3	92.6	103.6	199.1	77.8	119.7	92.2	103.2	197.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K5-532AXSP16	72.5	113.3	86.8	97.5	189.1	72.5	112.7	86.4	97	187.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K5-625AXSP16	85.4	130.6	100.9	112.8	213.3	85.4	129.7	100.6	112.3	211.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K5-632AXSP16	80.9	125	96.1	107.9	206.2	80.9	124.3	95.9	107.3	204.2	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K8-425AXSP16	71.5	111.6	85.3	95.9	186.3	71.5	110.9	85.1	95.4	184.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K8-432AXSP16	65.9	103.6	79	89	174.4	65.9	103.1	78.9	88.6	173	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K8-525AXSP16	77.8	120.3	92.6	103.6	199.1	77.8	119.7	92.2	103.2	197.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K8-532AXSP16	72.5	113.3	86.8	97.5	189.1	72.5	112.7	86.4	97	187.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K8-625AXSP16	85.4	130.6	100.9	112.8	213.3	85.4	129.7	100.6	112.3	211.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K8-632AXSP16	80.9	125	96.1	107.9	206.2	80.9	124.3	95.9	107.3	204.2	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K9-425AXSP16	71.5	111.6	85.3	95.9	186.3	71.5	110.9	85.1	95.4	184.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K9-432AXSP16	65.9	103.6	79	89	174.4	65.9	103.1	78.9	88.6	173	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750K9-525AXSP16	77.8	120.3	92.6	103.6	199.1	77.8	119.7	92.2	103.2	197.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K9-532AXSP16	72.5	113.3	86.8	97.5	189.1	72.5	112.7	86.4	97	187.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750K9-625AXSP16	85.4	130.6	100.9	112.8	213.3	85.4	129.7	100.6	112.3	211.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750K9-632AXSP16	80.9	125	96.1	107.9	206.2	80.9	124.3	95.9	107.3	204.2	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750R3-425AXSP16	70	109.1	83.4	93.8	182.3	70	108.6	83.2	93.5	180.8	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750R3-432AXSP16	64.6	101.6	77.4	87.2	170.8	64.6	101.1	77.3	86.8	169.5	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD15S1P1750R3-525AXSP16	76	117.7	90.4	101.4	194.5	76	116.9	90.1	100.8	192.7	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750R3-532AXSP16	71.1	110.9	84.9	95.3	184.7	71	110.2	84.5	95	183.2	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD15S1P1750R3-625AXSP16	83.3	127.5	98.5	110.1	207.9	83.4	126.7	98.1	109.5	206.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1P1750R3-632AXSP16	79.1	122.3	93.9	105.4	201.2	79.1	121.6	93.7	104.8	199.3	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD15S1PK370C2-425AXSP16	55.2	87.2	66.4	75	146.2	55.4	87	66.3	74.8	145.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK370C2-432AXSP16	51	81.3	61.6	69.6	137.3	51.2	81	61.5	69.4	136.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK370C2-525AXSP16	59.9	93.9	71.7	80.7	155.8	60.1	93.6	71.6	80.5	154.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK370C2-532AXSP16	56	88.8	67.4	76.1	148.4	56.2	88.3	67.3	75.8	147.2	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK370C2-625AXSP16	65.5	101.4	77.9	87.3	166.2	65.8	100.9	77.8	87.1	164.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK370C2-632AXSP16	62.2	97.4	74.4	83.7	161.2	62.5	96.9	74.4	83.5	159.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK370C4-425AXSP16	55.2	87.2	66.4	75	146.2	55.4	87	66.3	74.8	145.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK370C4-432AXSP16	51	81.3	61.6	69.6	137.3	51.2	81	61.5	69.4	136.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK370C4-525AXSP16	59.9	93.9	71.7	80.7	155.8	60.1	93.6	71.6	80.5	154.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK370C4-532AXSP16	56	88.8	67.4	76.1	148.4	56.2	88.3	67.3	75.8	147.2	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK370C4-625AXSP16	65.5	101.4	77.9	87.3	166.2	65.8	100.9	77.8	87.1	164.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK370C4-632AXSP16	62.2	97.4	74.4	83.7	161.2	62.5	96.9	74.4	83.5	159.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK370C5-425AXSP16	55.2	87.2	66.4	75	146.2	55.4	87	66.3	74.8	145.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK370C5-432AXSP16	51	81.3	61.																

EAW-VD15S1PK400B3-632AXSP16	60.4	94.5	72.2	81.1	156.1	60.7	94	72	80.8	154.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400C3-425AXSP16	55.2	87.2	66.4	75	146.2	55.4	87	66.3	74.8	145.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400C3-432AXSP16	51	81.3	61.6	69.6	137.3	51.2	81	61.5	69.4	136.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400C3-525AXSP16	59.9	93.9	71.7	80.7	155.8	60.1	93.6	71.6	80.5	154.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400C3-532AXSP16	56	88.8	67.4	76.1	148.4	56.2	88.3	67.3	75.8	147.2	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400C3-625AXSP16	65.5	101.4	77.9	87.3	166.2	65.8	100.9	77.8	87.1	164.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400C3-632AXSP16	62.2	97.4	74.4	83.7	161.2	62.5	96.9	74.4	83.5	159.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400C9-425AXSP16	55.2	87.2	66.4	75	146.2	55.4	87	66.3	74.8	145.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400C9-432AXSP16	51	81.3	61.6	69.6	137.3	51.2	81	61.5	69.4	136.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400C9-525AXSP16	59.9	93.9	71.7	80.7	155.8	60.1	93.6	71.6	80.5	154.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400C9-532AXSP16	56	88.8	67.4	76.1	148.4	56.2	88.3	67.3	75.8	147.2	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400C9-625AXSP16	65.5	101.4	77.9	87.3	166.2	65.8	100.9	77.8	87.1	164.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400C9-632AXSP16	62.2	97.4	74.4	83.7	161.2	62.5	96.9	74.4	83.5	159.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400K3-425AXSP16	53.2	83.9	63.9	72.1	140.4	53.3	83.5	63.8	71.9	139.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400K3-432AXSP16	49.1	78.4	59.4	67.1	132.2	49.3	78.1	59.3	66.9	131.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400K3-525AXSP16	57.6	90.2	68.9	77.4	149.5	57.8	89.7	68.8	77.3	148.1	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400K3-532AXSP16	53.9	85.3	64.9	73.1	142.6	54.1	84.9	64.8	72.9	141.4	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400K3-625AXSP16	62.9	97.2	74.7	83.7	159.1	63.1	96.7	74.6	83.5	157.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400K3-632AXSP16	59.8	93.5	71.5	80.3	154.6	60.1	93	71.4	80.1	153.3	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400K9-425AXSP16	53.2	83.9	63.9	72.1	140.4	53.3	83.5	63.8	71.9	139.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400K9-432AXSP16	49.1	78.4	59.4	67.1	132.2	49.3	78.1	59.3	66.9	131.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400K9-525AXSP16	57.6	90.2	68.9	77.4	149.5	57.8	89.7	68.8	77.3	148.1	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400K9-532AXSP16	53.9	85.3	64.9	73.1	142.6	54.1	84.9	64.8	72.9	141.4	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400K9-625AXSP16	62.9	97.2	74.7	83.7	159.1	63.1	96.7	74.6	83.5	157.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400K9-632AXSP16	59.8	93.5	71.5	80.3	154.6	60.1	93	71.4	80.1	153.3	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400R3-425AXSP16	54.2	85.6	65.1	73.4	143.3	54.3	85.2	65.1	73.2	142.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400R3-432AXSP16	50	79.9	60.4	68.4	134.7	50.3	79.6	60.5	68.1	133.7	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK400R3-525AXSP16	58.6	91.8	70.1	78.9	152.1	58.8	91.4	70	78.7	150.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400R3-532AXSP16	54.9	86.9	66.1	74.4	145.2	55.1	86.5	66	74.3	144.1	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK400R3-625AXSP16	64	98.9	76	85.2	162	64.2	98.4	76	84.9	160.6	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK400R3-632AXSP16	60.9	95.2	72.7	81.8	157.4	61.1	94.7	72.7	81.6	156.2	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550B3-425AXSP16	59	93.2	70.9	80	156.5	59.1	92.9	70.9	79.7	155.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550B3-432AXSP16	54.4	86.8	65.8	74.4	146.7	54.6	86.6	65.7	74.2	145.7	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550B3-525AXSP16	63.7	100	76.3	86	166.2	64	99.6	76.3	85.8	165.1	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550B3-532AXSP16	59.7	94.6	71.8	81.1	158.5	60	94.3	71.8	81	157.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550B3-625AXSP16	69.6	107.9	82.8	92.8	177	69.9	107.6	82.8	92.7	175.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550B3-632AXSP16	66.3	103.9	79.2	89.2	172.1	66.5	103.5	79.2	89	170.7	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C2-425AXSP16	61.9	97.9	74.5	83.9	164.5	62.1	97.5	74.4	83.7	163.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C2-432AXSP16	56.9	90.8	68.8	77.7	153.8	57.1	90.5	68.7	77.7	152.7	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C2-525AXSP16	67.4	105.7	80.8	91	176	67.6	105.3	80.6	90.7	174.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C2-532AXSP16	62.7	99.5	75.6	85.3	166.8	62.9	99.1	75.4	85.1	165.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C2-625AXSP16	74.1	115	88.2	99	189	74.3	114.5	88.1	98.7	187.7	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C2-632AXSP16	70	110	83.9	94.3	182.3	70.2	109.5	83.8	94.1	180.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C3-425AXSP16	61.9	97.9	74.5	83.9	164.5	62.1	97.5	74.4	83.7	163.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C3-432AXSP16	56.9	90.8	68.8	77.7	153.8	57.1	90.5	68.7	77.7	152.7	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C3-525AXSP16	67.4	105.7	80.8	91	176	67.6	105.3	80.6	90.7	174.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C3-532AXSP16	62.7	99.5	75.6	85.3	166.8	62.9	99.1	75.4	85.1	165.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C3-625AXSP16	74.1	115	88.2	99	189	74.3	114.5	88.1	98.7	187.7	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C3-632AXSP16	70	110	83.9	94.3	182.3	70.2	109.5	83.8	94.1	180.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C4-425AXSP16	61.9	97.9	74.5	83.9	164.5	62.1	97.5	74.4	83.7	163.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C4-432AXSP16	56.9	90.8	68.8	77.7	153.8	57.1	90.5	68.7	77.7	152.7	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C4-525AXSP16	67.4	105.7	80.8	91	176	67.6	105.3	80.6	90.7	174.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C4-532AXSP16	62.7	99.5	75.6	85.3	166.8	62.9	99.1	75.4	85.1	165.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C4-625AXSP16	74.1	115	88.2	99	189	74.3	114.5	88.1	98.7	187.7	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C4-632AXSP16	70	110	83.9	94.3	182.3	70.2	109.5	83.8	94.1	180.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C5-425AXSP16	61.9	97.9	74.5	83.9	164.5	62.1	97.5	74.4	83.7	163.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C5-432AXSP16	56.9	90.8	68.8	77.7	153.8	57.1	90.5	68.7	77.7	152.7	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550C5-525AXSP16	67.4	105.7	80.8	91	176	67.6	105.3	80.6	90.7	174.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C5-532AXSP16	62.7	99.5	75.6	85.3	166.8	62.9	99.1	75.4	85.1	165.8	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550C5-625AXSP16	74.1	115	88.2	99	189	74.3	114.5	88.1	98.7	187.7	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C5-632AXSP16	70	110	83.9	94.3	182.3	70.2	109.5	83.8	94.1	180.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550C8-425AXSP16	61.9	97.9	74.5	83.9	164.5	62.1	97.5	74.4	83.7	163.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"

EAW-VD15S1PK550K8-625AXSP16	70.3	109	83.6	93.8	178.9	70.5	108.6	83.5	93.5	177.5	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550K8-632AXSP16	66.2	104.5	79.8	89.7	173.1	67	104	79.7	89.6	171.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550K9-425AXSP16	59.6	93.6	71.1	80.3	157.2	59.3	93.2	71.2	80	156.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550K9-432AXSP16	54.6	87	65.9	74.6	147.1	54.8	86.7	65.9	74.5	146.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550K9-525AXSP16	64.1	100.7	76.8	86.5	167.4	64.3	100.3	76.8	86.3	166.1	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550K9-532AXSP16	60	95	72.1	81.5	159.2	60.2	94.6	72.1	81.3	158	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550K9-625AXSP16	70.3	109	83.6	93.8	178.9	70.5	108.6	83.5	93.5	177.5	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550K9-632AXSP16	66.6	104.5	79.8	89.7	173.1	67	104	79.7	89.6	171.9	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550R3-425AXSP16	60.7	95.9	73	82.3	161.3	60.9	95.7	73	82.2	160.3	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550R3-432AXSP16	55.9	89.3	67.6	76.5	150.9	56.2	88.9	67.6	76.3	150.2	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK550R3-525AXSP16	65.7	103.1	78.8	88.7	171.6	66.1	102.8	78.8	88.5	170.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550R3-532AXSP16	61.4	97.4	73.9	83.6	163.5	61.7	97.1	74	83.4	162.4	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK550R3-625AXSP16	72	111.8	85.8	96.3	183.6	72.4	111.4	85.7	96	182.4	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK550R3-632AXSP16	68.4	107.2	81.8	92.1	177.7	68.7	106.8	81.8	91.9	176.5	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C2-425AXSP16	65.8	104.2	79.2	89.3	175.5	66.1	104	79.3	89.3	174.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C2-432AXSP16	60.6	96.7	73.3	82.8	164.1	60.9	96.6	73.3	82.7	163.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C2-525AXSP16	71.5	112.4	85.8	96.6	187.5	71.9	112	85.8	96.4	186.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C2-532AXSP16	66.6	105.7	80.3	90.7	177.9	67	105.5	80.3	90.5	176.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C2-625AXSP16	78.5	121.9	93.5	104.9	201	78.9	121.6	93.6	104.8	199.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C2-632AXSP16	74.3	116.8	89	100.2	194.2	74.6	116.5	89.1	100.1	192.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C3-425AXSP16	65.8	104.2	79.2	89.3	175.5	66.1	104	79.3	89.3	174.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C3-432AXSP16	60.6	96.7	73.3	82.8	164.1	60.9	96.6	73.3	82.7	163.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C3-525AXSP16	71.5	112.4	85.8	96.6	187.5	71.9	112	85.8	96.4	186.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C3-532AXSP16	66.6	105.7	80.3	90.7	177.9	67	105.5	80.3	90.5	176.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C3-625AXSP16	78.5	121.9	93.5	104.9	201	78.9	121.6	93.6	104.8	199.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C3-632AXSP16	74.3	116.8	89	100.2	194.2	74.6	116.5	89.1	100.1	192.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C4-425AXSP16	65.8	104.2	79.2	89.3	175.5	66.1	104	79.3	89.3	174.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C4-432AXSP16	60.6	96.7	73.3	82.8	164.1	60.9	96.6	73.3	82.7	163.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C4-525AXSP16	71.5	112.4	85.8	96.6	187.5	71.9	112	85.8	96.4	186.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C4-532AXSP16	66.6	105.7	80.3	90.7	177.9	67	105.5	80.3	90.5	176.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C4-625AXSP16	78.5	121.9	93.5	104.9	201	78.9	121.6	93.6	104.8	199.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C4-632AXSP16	74.3	116.8	89	100.2	194.2	74.6	116.5	89.1	100.1	192.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C5-425AXSP16	65.8	104.2	79.2	89.3	175.5	66.1	104	79.3	89.3	174.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C5-432AXSP16	60.6	96.7	73.3	82.8	164.1	60.9	96.6	73.3	82.7	163.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C5-525AXSP16	71.5	112.4	85.8	96.6	187.5	71.9	112	85.8	96.4	186.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C5-532AXSP16	66.6	105.7	80.3	90.7	177.9	67	105.5	80.3	90.5	176.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C5-625AXSP16	78.5	121.9	93.5	104.9	201	78.9	121.6	93.6	104.8	199.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C5-632AXSP16	74.3	116.8	89	100.2	194.2	74.6	116.5	89.1	100.1	192.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C8-425AXSP16	65.8	104.2	79.2	89.3	175.5	66.1	104	79.3	89.3	174.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C8-432AXSP16	60.6	96.7	73.3	82.8	164.1	60.9	96.6	73.3	82.7	163.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C8-525AXSP16	71.5	112.4	85.8	96.6	187.5	71.9	112	85.8	96.4	186.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C8-532AXSP16	66.6	105.7	80.3	90.7	177.9	67	105.5	80.3	90.5	176.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C8-625AXSP16	78.5	121.9	93.5	104.9	201	78.9	121.6	93.6	104.8	199.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C8-632AXSP16	74.3	116.8	89	100.2	194.2	74.6	116.5	89.1	100.1	192.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C9-425AXSP16	65.8	104.2	79.2	89.3	175.5	66.1	104	79.3	89.3	174.5	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C9-432AXSP16	60.6	96.7	73.3	82.8	164.1	60.9	96.6	73.3	82.7	163.1	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750C9-525AXSP16	71.5	112.4	85.8	96.6	187.5	71.9	112	85.8	96.4	186.5	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C9-532AXSP16	66.6	105.7	80.3	90.7	177.9	67	105.5	80.3	90.5	176.9	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750C9-625AXSP16	78.5	121.9	93.5	104.9	201	78.9	121.6	93.6	104.8	199.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750C9-632AXSP16	74.3	116.8	89	100.2	194.2	74.6	116.5	89.1	100.1	192.8	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750K2-425AXSP16	63.6	100.7	76.7	86.4	169.7	63.9	100.6	76.8	86.3	168.8	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750K2-432AXSP16	58.7	93.7	70.9	80.1	158.7	58.9	93.4	71	80.2	157.8	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750K2-525AXSP16	69	108.3	82.7	93.2	180.5	69.3	108.1	82.8	93	179.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750K2-532AXSP16	64.4	102.1	77.6	87.6	171.7	64.8	102	77.6	87.6	170.7	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750K2-625AXSP16	75.6	117.5	90.1	101.1	193.3	76	117.1	90.1	100.9	192	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750K2-632AXSP16	71.7	112.6	85.8	96.7	187	72.1	112.3	85.9	96.6	185.7	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750K3-425AXSP16	63.6	100.7	76.7	86.4	169.7	63.9	100.6	76.8	86.3	168.8	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750K3-432AXSP16	58.7	93.7	70.9	80.1	158.7	58.9	93.4	71	80.2	157.8	113	18.4	1-1/2"	90	12.1	1-1/2"	135	25.9	1-1/2"
EAW-VD15S1PK750K3-525AXSP16	69	108.3	82.7	93.2	180.5	69.3	108.1	82.8	93	179.6	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750K3-532AXSP16	64.4	102.1	77.6	87.6	171.7	64.8	102	77.6	87.6	170.7	135	19.8	1-1/2"	108	13.1	1-1/2"	162	23.6	2"
EAW-VD15S1PK750K3-625AXSP16	75.6	117.5	90.1	101.1	193.3	76	117.1	90.1	100.9	192	169	17.7	2"	135	14.7	1-1/2"	203	24.9	2"
EAW-VD15S1PK750K3-632AXSP16	71.7	112.6	85.8	96.7	187	72.1	112.3	85.9	96.6	185.7</									

EAW-VD15S1ZB370C4-532AXSP16	-	95.2	72.1	81.4	159.6	-	94.6	71.9	81.2	158.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370C4-625AXSP16	-	109.3	83.7	94	179.8	-	108.6	83.5	93.6	178	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370C4-632AXSP16	-	104.6	79.7	89.7	173.9	-	104.1	79.6	89.4	172.1	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370C5-425AXSP16	57.9	92.4	69.9	79	155.1	58.2	91.9	69.8	78.7	153.8	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370C5-432AXSP16	53.3	85.8	64.6	73.2	145.3	53.5	85.4	64.6	73.1	144.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370C5-525AXSP16	64	100.9	76.8	86.5	167.8	64.2	100.4	76.7	86.3	166.4	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370C5-532AXSP16	-	95.2	72.1	81.4	159.6	-	94.6	71.9	81.2	158.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370C5-625AXSP16	-	109.3	83.7	94	179.8	-	108.6	83.5	93.6	178	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370C5-632AXSP16	-	104.6	79.7	89.7	173.9	-	104.1	79.6	89.4	172.1	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370C8-425AXSP16	57.9	92.4	69.9	79	155.1	58.2	91.9	69.8	78.7	153.8	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370C8-432AXSP16	53.3	85.8	64.6	73.2	145.3	53.5	85.4	64.6	73.1	144.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370C8-525AXSP16	64	100.9	76.8	86.5	167.8	64.2	100.4	76.7	86.3	166.4	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370C8-532AXSP16	-	95.2	72.1	81.4	159.6	-	94.6	71.9	81.2	158.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370C8-625AXSP16	-	109.3	83.7	94	179.8	-	108.6	83.5	93.6	178	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370C8-632AXSP16	-	104.6	79.7	89.7	173.9	-	104.1	79.6	89.4	172.1	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K2-425AXSP16	55.7	88.9	67.3	76.1	149.2	56	88.5	67.2	75.8	147.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K2-432AXSP16	51.5	82.8	62.3	70.6	140	51.7	82.3	62.4	70.5	138.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K2-525AXSP16	61.4	96.8	73.7	83.1	160.8	61.6	96.3	73.6	82.7	159.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K2-532AXSP16	-	91.5	69.3	78.3	153.5	-	91	69.3	78	151.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K2-632AXSP16	-	104.5	80.1	90	171.8	-	104	80	89.6	169.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K2-632AXSP16	-	100.3	76.5	86	166.4	-	99.7	76.4	85.7	164.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K4-425AXSP16	55.7	88.9	67.3	76.1	149.2	56	88.5	67.2	75.8	147.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K4-432AXSP16	51.5	82.8	62.3	70.6	140	51.7	82.3	62.4	70.5	138.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K4-525AXSP16	61.4	96.8	73.7	83.1	160.8	61.6	96.3	73.6	82.7	159.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K4-532AXSP16	-	91.5	69.3	78.3	153.5	-	91	69.3	78	151.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K4-625AXSP16	-	104.5	80.1	90	171.8	-	104	80	89.6	169.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K4-632AXSP16	-	100.3	76.5	86	166.4	-	99.7	76.4	85.7	164.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K5-425AXSP16	55.7	88.9	67.3	76.1	149.2	56	88.5	67.2	75.8	147.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K5-432AXSP16	51.5	82.8	62.3	70.6	140	51.7	82.3	62.4	70.5	138.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K5-525AXSP16	61.4	96.8	73.7	83.1	160.8	61.6	96.3	73.6	82.7	159.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K5-532AXSP16	-	91.5	69.3	78.3	153.5	-	91	69.3	78	151.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K5-625AXSP16	-	104.5	80.1	90	171.8	-	104	80	89.6	169.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K5-632AXSP16	-	100.3	76.5	86	166.4	-	99.7	76.4	85.7	164.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K8-425AXSP16	55.7	88.9	67.3	76.1	149.2	56	88.5	67.2	75.8	147.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K8-432AXSP16	51.5	82.8	62.3	70.6	140	51.7	82.3	62.4	70.5	138.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB370K8-525AXSP16	61.4	96.8	73.7	83.1	160.8	61.6	96.3	73.6	82.7	159.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K8-532AXSP16	-	91.5	69.3	78.3	153.5	-	91	69.3	78	151.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB370K8-625AXSP16	-	104.5	80.1	90	171.8	-	104	80	89.6	169.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB370K8-632AXSP16	-	100.3	76.5	86	166.4	-	99.7	76.4	85.7	164.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400B3-425AXSP16	56.5	90.1	68.2	77.1	151.1	56.7	89.6	68.2	76.9	149.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400B3-432AXSP16	52.2	83.8	63.2	71.6	141.8	52.4	83.5	63.2	71.5	140.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400B3-525AXSP16	62.3	98.1	74.7	84.2	163.1	62.6	97.6	74.7	83.9	161.7	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400B3-532AXSP16	-	92.8	70.2	79.4	155.5	-	92.3	70.2	79.1	154.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400B3-625AXSP16	-	105.8	81.1	91	174	-	105.2	81	90.7	172.2	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400B3-632AXSP16	-	101.7	77.5	87.3	168.8	-	101.1	77.5	87	167.3	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400C3-425AXSP16	57.9	92.4	69.9	79	155.1	58.2	91.9	69.8	78.7	153.8	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400C3-432AXSP16	53.3	85.8	64.6	73.2	145.3	53.5	85.4	64.6	73.1	144.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400C3-525AXSP16	64	100.9	76.8	86.5	167.8	64.2	100.4	76.7	86.3	166.4	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400C3-532AXSP16	-	95.2	72.1	81.4	159.6	-	94.6	71.9	81.2	158.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400C3-625AXSP16	-	109.3	83.7	94	179.8	-	108.6	83.5	93.6	178	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400C3-632AXSP16	-	104.6	79.7	89.7	173.9	-	104.1	79.6	89.4	172.1	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400C9-425AXSP16	57.9	92.4	69.9	79	155.1	58.2	91.9	69.8	78.7	153.8	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400C9-432AXSP16	53.3	85.8	64.6	73.2	145.3	53.5	85.4	64.6	73.1	144.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400C9-525AXSP16	64	100.9	76.8	86.5	167.8	64.2	100.4	76.7	86.3	166.4	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400C9-532AXSP16	-	95.2	72.1	81.4	159.6	-	94.6	71.9	81.2	158.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400C9-625AXSP16	-	109.3	83.7	94	179.8	-	108.6	83.5	93.6	178	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400C9-632AXSP16	-	104.6	79.7	89.7	173.9	-	104.1	79.6	89.4	172.1	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400K3-425AXSP16	55.7	88.9	67.3	76.1	149.2	56	88.5	67.2	75.8	147.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400K3-432AXSP16	51.5	82.8	62.3	70.6	140	51.7	82.3	62.4	70.5	138.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400K3-525AXSP16	61.4	96.8	73.7	83.1	160.8	61.6	96.3	73.6	82.7	159.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400K3-532AXSP16	-	91.5	69.3	78.3	153.5	-	91	69.3	78	151.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB400K3-625AXSP16	-	104.5	80.1	90	171.8	-	104	80	89.6	169.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400K3-632AXSP16	-	100.3	76.5	86	166.4	-	99.7	76.4	85.7	164.9	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB400K9-425AXSP16	55.7	88.9	67.3	76.1	149.2	56	88.5	67.2	75.8	147.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB400K9-432AXSP16	51.5	82.8	62.3	70.6	140	51.7	82.3	62.4	70.5	138.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S																			

EAW-VD15S1ZB550C5-525AXSP16	72.2	114.3	86.9	97.9	190.5	72.4	113.8	86.8	97.6	189	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550C5-532AXSP16	67	107.2	81.1	91.7	180.3	67.4	106.7	81	91.4	178.8	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550C5-625AXSP16	79.6	124.4	95.1	106.9	205.1	79.9	123.7	95	106.6	203.2	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550C5-632AXSP16	-	118.4	90.2	101.5	197.2	75.4	117.9	90	101.3	195.6	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550C8-425AXSP16	65	103.9	78.7	88.9	174.9	65.2	103.5	78.6	88.7	173.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550C8-432AXSP16	59.6	96.2	72.4	82.2	163.2	60	95.9	72.4	81.9	162	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550C8-525AXSP16	72.2	114.3	86.9	97.9	190.5	72.4	113.8	86.8	97.6	189	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550C8-532AXSP16	67	107.2	81.1	91.7	180.3	67.4	106.7	81	91.4	178.8	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550C8-625AXSP16	79.6	124.4	95.1	106.9	205.1	79.9	123.7	95	106.6	203.2	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550C8-632AXSP16	-	118.4	90.2	101.5	197.2	75.4	117.9	90	101.3	195.6	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550C9-425AXSP16	65	103.9	78.7	88.9	174.9	65.2	103.5	78.6	88.7	173.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550C9-432AXSP16	59.6	96.2	72.4	82.2	163.2	60	95.9	72.4	81.9	162	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550C9-525AXSP16	72.2	114.3	86.9	97.9	190.5	72.4	113.8	86.8	97.6	189	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550C9-532AXSP16	67	107.2	81.1	91.7	180.3	67.4	106.7	81	91.4	178.8	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550C9-632AXSP16	79.6	124.4	95.1	106.9	205.1	79.9	123.7	95	106.6	203.2	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550C9-632AXSP16	-	118.4	90.2	101.5	197.2	75.4	117.9	90	101.3	195.6	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K2-425AXSP16	62.3	99.6	75.3	85.1	167.3	62.6	99.2	75.3	85	166.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K2-432AXSP16	57.4	92.5	69.7	78.9	156.6	57.6	92.1	69.7	78.7	155.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K2-525AXSP16	68.8	109	82.8	93.3	181.3	69.2	108.5	82.7	93.1	179.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K2-532AXSP16	64.2	102.6	77.6	87.8	172.3	64.6	102.2	77.6	87.5	171	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K2-625AXSP16	75.7	118	90.4	101.5	194.5	76.1	117.4	90.3	101.2	192.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K2-632AXSP16	-	112.9	86	96.9	187.8	-	112.3	85.9	96.5	186	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K3-425AXSP16	62.3	99.6	75.3	85.1	167.3	62.6	99.2	75.3	85	166.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K3-432AXSP16	57.4	92.5	69.7	78.9	156.6	57.6	92.1	69.7	78.7	155.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K3-525AXSP16	68.8	109	82.8	93.3	181.3	69.2	108.5	82.7	93.1	179.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K3-532AXSP16	64.2	102.6	77.6	87.8	172.3	64.6	102.2	77.6	87.5	171	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K3-632AXSP16	75.7	118	90.4	101.5	194.5	76.1	117.4	90.3	101.2	192.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K3-632AXSP16	-	112.9	86	96.9	187.8	-	112.3	85.9	96.5	186	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K4-425AXSP16	62.3	99.6	75.3	85.1	167.3	62.6	99.2	75.3	85	166.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K4-432AXSP16	57.4	92.5	69.7	78.9	156.6	57.6	92.1	69.7	78.7	155.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K4-525AXSP16	68.8	109	82.8	93.3	181.3	69.2	108.5	82.7	93.1	179.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K4-532AXSP16	64.2	102.6	77.6	87.8	172.3	64.6	102.2	77.6	87.5	171	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K4-625AXSP16	75.7	118	90.4	101.5	194.5	76.1	117.4	90.3	101.2	192.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K4-632AXSP16	-	112.9	86	96.9	187.8	-	112.3	85.9	96.5	186	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K5-425AXSP16	62.3	99.6	75.3	85.1	167.3	62.6	99.2	75.3	85	166.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K5-432AXSP16	57.4	92.5	69.7	78.9	156.6	57.6	92.1	69.7	78.7	155.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K5-525AXSP16	68.8	109	82.8	93.3	181.3	69.2	108.5	82.7	93.1	179.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K5-532AXSP16	64.2	102.6	77.6	87.8	172.3	64.6	102.2	77.6	87.5	171	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K5-625AXSP16	75.7	118	90.4	101.5	194.5	76.1	117.4	90.3	101.2	192.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K5-632AXSP16	-	112.9	86	96.9	187.8	-	112.3	85.9	96.5	186	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K8-425AXSP16	62.3	99.6	75.3	85.1	167.3	62.6	99.2	75.3	85	166.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K8-432AXSP16	57.4	92.5	69.7	78.9	156.6	57.6	92.1	69.7	78.7	155.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K8-525AXSP16	68.8	109	82.8	93.3	181.3	69.2	108.5	82.7	93.1	179.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K8-532AXSP16	64.2	102.6	77.6	87.8	172.3	64.6	102.2	77.6	87.5	171	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K8-625AXSP16	75.7	118	90.4	101.5	194.5	76.1	117.4	90.3	101.2	192.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K8-632AXSP16	-	112.9	86	96.9	187.8	-	112.3	85.9	96.5	186	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K9-425AXSP16	62.3	99.6	75.3	85.1	167.3	62.6	99.2	75.3	85	166.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K9-432AXSP16	57.4	92.5	69.7	78.9	156.6	57.6	92.1	69.7	78.7	155.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550K9-525AXSP16	68.8	109	82.8	93.3	181.3	69.2	108.5	82.7	93.1	179.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K9-532AXSP16	64.2	102.6	77.6	87.8	172.3	64.6	102.2	77.6	87.5	171	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550K9-625AXSP16	75.7	118	90.4	101.5	194.5	76.1	117.4	90.3	101.2	192.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550K9-632AXSP16	-	112.9	86	96.9	187.8	-	112.3	85.9	96.5	186	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550R3-425AXSP16	64	102.3	77.4	87.5	172.1	64.4	101.8	77.3	87.4	170.9	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550R3-432AXSP16	58.9	95	71.6	81.2	161.1	59.2	94.8	71.6	81	160	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB550R3-525AXSP16	70.7	112	85.1	95.9	186.7	71.2	111.5	85.1	95.7	185.1	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550R3-532AXSP16	66	105.4	79.8	90.1	177.2	66.4	105	79.8	89.9	175.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB550R3-625AXSP16	77.7	121.5	93	104.4	200.3	78.2	120.8	92.9	104.1	198.4	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB550R3-632AXSP16	-	116.2	88.4	99.6	193.3	-	115.6	88.3	99.3	191.6	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750C2-425AXSP16	69.8	111.5	84.3	95.5	188.2	70	111	84.3	95.3	187	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750C2-432AXSP16	64	103.2	77.7	88.1	175.4	64.3	102.9	77.8	88	174.1	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750C2-525AXSP16	77.3	122.5	93	105.1	204.6	77.7	122.1	93.1	104.8	203.3	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750C2-532AXSP16	71.9	115	86.9	98.4	193.7	72.3	114.7	87	98.1	192.4	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750C2-625AXSP16	85.2	133.3	101.9	114.5	220.2	85.6	132.8	101.8	114.3	218.4	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750C2-632AXSP16	80.4	127.2	96.7	108.9	212	80.8	126.8	96.7	108.9	210.3	225	18.8	2						

EAW-VD15S1ZB750K3-432AXSP16	62	100	75.3	85.4	169.6	62.3	99.6	75.4	85.3	168.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K3-525AXSP16	74.6	118.2	89.7	101.4	197.2	75	117.8	89.8	101.2	195.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K3-532AXSP16	69.4	111	84	94.9	187	69.9	110.7	84.1	94.8	185.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K3-625AXSP16	82.1	128.3	98	110.2	211.8	82.5	127.7	98	110	210	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K3-632AXSP16	77.6	122.6	93.2	105.1	204.4	77.9	122.1	93.3	104.9	202.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K4-425AXSP16	67.4	107.9	81.5	92.3	181.8	67.8	107.4	81.5	92.1	180.4	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K4-432AXSP16	62	100	75.3	85.4	169.6	62.3	99.6	75.4	85.3	168.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K4-525AXSP16	74.6	118.2	89.7	101.4	197.2	75	117.8	89.8	101.2	195.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K4-532AXSP16	69.4	111	84	94.9	187	69.9	110.7	84.1	94.8	185.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K4-625AXSP16	82.1	128.3	98	110.2	211.8	82.5	127.7	98	110	210	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K4-632AXSP16	77.6	122.6	93.2	105.1	204.4	77.9	122.1	93.3	104.9	202.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K5-425AXSP16	67.4	107.9	81.5	92.3	181.8	67.8	107.4	81.5	92.1	180.4	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K5-432AXSP16	62	100	75.3	85.4	169.6	62.3	99.6	75.4	85.3	168.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K5-525AXSP16	74.6	118.2	89.7	101.4	197.2	75	117.8	89.8	101.2	195.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K5-532AXSP16	69.4	111	84	94.9	187	69.9	110.7	84.1	94.8	185.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K5-625AXSP16	82.1	128.3	98	110.2	211.8	82.5	127.7	98	110	210	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K5-632AXSP16	77.6	122.6	93.2	105.1	204.4	77.9	122.1	93.3	104.9	202.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K8-425AXSP16	67.4	107.9	81.5	92.3	181.8	67.8	107.4	81.5	92.1	180.4	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K8-432AXSP16	62	100	75.3	85.4	169.6	62.3	99.6	75.4	85.3	168.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K8-525AXSP16	74.6	118.2	89.7	101.4	197.2	75	117.8	89.8	101.2	195.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K8-532AXSP16	69.4	111	84	94.9	187	69.9	110.7	84.1	94.8	185.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K8-625AXSP16	82.1	128.3	98	110.2	211.8	82.5	127.7	98	110	210	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K8-632AXSP16	77.6	122.6	93.2	105.1	204.4	77.9	122.1	93.3	104.9	202.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K9-425AXSP16	67.4	107.9	81.5	92.3	181.8	67.8	107.4	81.5	92.1	180.4	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K9-432AXSP16	62	100	75.3	85.4	169.6	62.3	99.6	75.4	85.3	168.7	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750K9-525AXSP16	74.6	118.2	89.7	101.4	197.2	75	117.8	89.8	101.2	195.9	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K9-532AXSP16	69.4	111	84	94.9	187	69.9	110.7	84.1	94.8	185.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750K9-625AXSP16	82.1	128.3	98	110.2	211.8	82.5	127.7	98	110	210	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750K9-632AXSP16	77.6	122.6	93.2	105.1	204.4	77.9	122.1	93.3	104.9	202.7	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750R3-425AXSP16	66	105.5	79.8	90.3	177.6	66.4	105.2	79.8	90.1	176.5	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750R3-432AXSP16	60.7	98.1	73.8	83.6	166.3	61.1	97.8	73.9	83.6	165	146	16.1	2"	117	13.1	1-1/2"	176	22.5	2"
EAW-VD15S1ZB750R3-525AXSP16	73	115.5	87.7	99	192.7	73.3	115.1	87.7	98.8	191.2	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750R3-532AXSP16	68	108.8	82.2	92.9	182.8	68.4	108.3	82.3	92.8	181.5	180	17.1	2"	144	11.3	2"	216	24.1	2"
EAW-VD15S1ZB750R3-625AXSP16	80.1	125.2	95.7	107.5	206.4	80.5	124.5	95.6	107.3	204.6	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZB750R3-632AXSP16	75.9	119.8	91.1	102.7	199.5	76.2	119.3	91.1	102.5	197.8	225	18.8	2"	180	12.4	2"	270	20.9	3"
EAW-VD15S1ZK017G7-425AXSP16	88.4	140.1	106.3	120	236.7	88.7	139.4	106.3	119.6	234.6	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK017G7-432AXSP16	80.5	128.6	97.4	110.1	218.6	80.7	128.2	97.3	109.8	216.8	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK017G7-525AXSP16	99.2	155.8	119	134	260.9	99.3	155.1	118.7	133.4	258.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK017G7-532AXSP16	91.4	144.8	110.1	124.2	244.2	91.5	144.3	109.9	124	242	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK017G7-625AXSP16	110.6	172.2	131.9	148.3	284.5	110.8	171.1	131.6	147.7	281.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK017G7-632AXSP16	103.2	162.4	123.7	139.4	270.5	103.4	161.4	123.6	138.9	267.9	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C2-425AXSP16	61.4	97	73.8	83.3	162	61.5	96.4	73.5	82.7	160.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C2-432AXSP16	56.6	90.3	68.3	77.1	151.7	56.7	89.7	68.1	76.9	150.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C2-525AXSP16	68	106.1	81.2	91.2	175.5	68	105.4	80.9	90.6	173.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C2-532AXSP16	63.4	100.1	76	85.8	166.7	63.5	99.2	75.8	85.3	165.1	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C2-625AXSP16	-	114.9	88.4	99	187.6	-	114	88	98.4	185.5	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C2-632AXSP16	-	109.9	84.2	94.5	181.5	-	109.1	83.9	94	179.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C4-425AXSP16	61.4	97	73.8	83.3	162	61.5	96.4	73.5	82.7	160.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C4-432AXSP16	56.6	90.3	68.3	77.1	151.7	56.7	89.7	68.1	76.9	150.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C4-525AXSP16	68	106.1	81.2	91.2	175.5	68	105.4	80.9	90.6	173.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C4-532AXSP16	63.4	100.1	76	85.8	166.7	63.5	99.2	75.8	85.3	165.1	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C4-625AXSP16	-	114.9	88.4	99	187.6	-	114	88	98.4	185.5	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C4-632AXSP16	-	109.9	84.2	94.5	181.5	-	109.1	83.9	94	179.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C5-425AXSP16	61.4	97	73.8	83.3	162	61.5	96.4	73.5	82.7	160.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C5-432AXSP16	56.6	90.3	68.3	77.1	151.7	56.7	89.7	68.1	76.9	150.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C5-525AXSP16	68	106.1	81.2	91.2	175.5	68	105.4	80.9	90.6	173.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C5-532AXSP16	63.4	100.1	76	85.8	166.7	63.5	99.2	75.8	85.3	165.1	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C5-625AXSP16	-	114.9	88.4	99	187.6	-	114	88	98.4	185.5	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C5-632AXSP16	-	109.9	84.2	94.5	181.5	-	109.1	83.9	94	179.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK370C8-425AXSP16	61.4	97	73.8	83.3	162	61.5	96.4	73.5	82.7	160.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C8-432AXSP16	56.6	90.3	68.3	77.1	151.7	56.7	89.7	68.1	76.9	150.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK370C8-525AXSP16	68	106.1	81.2	91.2	175.5	68	105.4	80.9	90.6	173.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C8-532AXSP16	63.4	100.1	76	85.8	166.7	63.5	99.2	75.8	85.3	165.1	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK370C8-625AXSP16	-	114.9	88.4	99	187.6	-	114	88	98.4	185.5	225	20	2"	180	13.2	2"	270		

EAW-VD15S1ZK400C9-425AXSP16	61.4	97	73.8	83.3	162	61.5	96.4	73.5	82.7	160.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400C9-432AXSP16	56.6	90.3	68.3	77.1	151.7	56.7	89.7	68.1	76.9	150.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400C9-525AXSP16	68	106.1	81.2	91.2	175.5	68	105.4	80.9	90.6	173.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400C9-532AXSP16	63.4	100.1	76	85.8	166.7	63.5	99.2	75.8	85.3	165.1	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400C9-625AXSP16	-	114.9	88.4	99	187.6	-	114	88	98.4	185.5	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400C9-632AXSP16	-	109.9	84.2	94.5	181.5	-	109.1	83.9	94	179.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400K3-425AXSP16	59.2	93.5	71.1	80.1	155.8	59.2	92.9	70.8	79.8	154.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400K3-432AXSP16	54.7	87.1	66	74.5	146.4	54.8	86.5	65.8	74.2	145.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400K3-525AXSP16	65.2	101.8	77.9	87.5	168.2	65.3	101.1	77.6	87.1	166.4	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400K3-532AXSP16	61.1	96.2	73.2	82.5	160.4	61.1	95.6	73	82.1	158.8	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400K3-625AXSP16	-	109.9	84.6	94.8	179.3	-	109.1	84.3	94.2	177.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400K3-632AXSP16	-	105.5	80.8	90.7	173.8	-	104.7	80.5	90.2	171.9	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400K9-425AXSP16	59.2	93.5	71.1	80.1	155.8	59.2	92.9	70.8	79.8	154.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400K9-432AXSP16	54.7	87.1	66	74.5	146.4	54.8	86.5	65.8	74.2	145.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400K9-525AXSP16	65.2	101.8	77.9	87.5	168.2	65.3	101.1	77.6	87.1	166.4	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400K9-532AXSP16	61.1	96.2	73.2	82.5	160.4	61.1	95.6	73	82.1	158.8	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400K9-625AXSP16	-	109.9	84.6	94.8	179.3	-	109.1	84.3	94.2	177.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400K9-632AXSP16	-	105.5	80.8	90.7	173.8	-	104.7	80.5	90.2	171.9	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400R3-425AXSP16	60.5	95.5	72.6	81.9	159.3	60.6	95	72.5	81.5	157.9	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400R3-432AXSP16	55.9	89.1	67.4	76.1	149.8	56	88.5	67.2	75.9	148.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK400R3-525AXSP16	66.7	104	79.6	89.5	171.9	66.7	103.3	79.3	88.9	170.1	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400R3-532AXSP16	62.4	98.3	74.9	84.3	164	62.5	97.7	74.7	83.9	162.4	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK400R3-625AXSP16	-	112.3	86.5	96.8	183.3	-	111.5	86.1	96.3	181.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK400R3-632AXSP16	-	107.8	82.5	92.7	177.8	-	107	82.2	92.3	175.9	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550B3-425AXSP16	66.2	104.7	79.6	89.8	175.2	66.3	104	79.4	89.4	173.5	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550B3-432AXSP16	60.9	97.3	73.7	83.2	163.9	61.1	96.9	73.4	82.9	162.6	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550B3-525AXSP16	73.2	114.6	87.5	98.4	189.6	73.3	113.8	87.3	97.9	188	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550B3-532AXSP16	68.3	107.9	82	92.5	180.2	68.5	107.3	81.9	92.1	178.6	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550B3-625AXSP16	80.3	124	95.3	106.8	202.8	80.4	123.1	95	106.3	200.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550B3-632AXSP16	76.1	118.7	90.8	102.1	196.3	76.2	118	90.6	101.6	194.3	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C2-425AXSP16	69.1	109.4	83.1	93.9	183.3	69.3	108.6	82.9	93.4	181.7	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C2-432AXSP16	63.4	101.3	76.6	86.7	171	63.5	100.7	76.4	86.3	169.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C2-525AXSP16	76.8	120.4	91.9	103.3	199.4	76.8	119.6	91.5	102.8	197.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C2-532AXSP16	71.4	113	85.8	96.7	188.7	71.5	112.2	85.6	96.3	187	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C2-625AXSP16	84.7	131	100.7	112.9	214.7	84.7	130	100.3	112.1	212.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C2-632AXSP16	79.9	124.9	95.4	107.3	206.5	79.9	123.8	95.1	106.7	204.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C3-425AXSP16	69.1	109.4	83.1	93.9	183.3	69.3	108.6	82.9	93.4	181.7	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C3-432AXSP16	63.4	101.3	76.6	86.7	171	63.5	100.7	76.4	86.3	169.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C3-525AXSP16	76.8	120.4	91.9	103.3	199.4	76.8	119.6	91.5	102.8	197.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C3-532AXSP16	71.4	113	85.8	96.7	188.7	71.5	112.2	85.6	96.3	187	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C3-625AXSP16	84.7	131	100.7	112.9	214.7	84.7	130	100.3	112.1	212.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C3-632AXSP16	79.9	124.9	95.4	107.3	206.5	79.9	123.8	95.1	106.7	204.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C4-425AXSP16	69.1	109.4	83.1	93.9	183.3	69.3	108.6	82.9	93.4	181.7	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C4-432AXSP16	63.4	101.3	76.6	86.7	171	63.5	100.7	76.4	86.3	169.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C4-525AXSP16	76.8	120.4	91.9	103.3	199.4	76.8	119.6	91.5	102.8	197.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C4-532AXSP16	71.4	113	85.8	96.7	188.7	71.5	112.2	85.6	96.3	187	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C4-625AXSP16	84.7	131	100.7	112.9	214.7	84.7	130	100.3	112.1	212.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C4-632AXSP16	79.9	124.9	95.4	107.3	206.5	79.9	123.8	95.1	106.7	204.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C5-425AXSP16	69.1	109.4	83.1	93.9	183.3	69.3	108.6	82.9	93.4	181.7	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C5-432AXSP16	63.4	101.3	76.6	86.7	171	63.5	100.7	76.4	86.3	169.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C5-525AXSP16	76.8	120.4	91.9	103.3	199.4	76.8	119.6	91.5	102.8	197.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C5-532AXSP16	71.4	113	85.8	96.7	188.7	71.5	112.2	85.6	96.3	187	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C5-625AXSP16	84.7	131	100.7	112.9	214.7	84.7	130	100.3	112.1	212.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C5-632AXSP16	79.9	124.9	95.4	107.3	206.5	79.9	123.8	95.1	106.7	204.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C8-425AXSP16	69.1	109.4	83.1	93.9	183.3	69.3	108.6	82.9	93.4	181.7	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C8-432AXSP16	63.4	101.3	76.6	86.7	171	63.5	100.7	76.4	86.3	169.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C8-525AXSP16	76.8	120.4	91.9	103.3	199.4	76.8	119.6	91.5	102.8	197.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C8-532AXSP16	71.4	113	85.8	96.7	188.7	71.5	112.2	85.6	96.3	187	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C8-625AXSP16	84.7	131	100.7	112.9	214.7	84.7	130	100.3	112.1	212.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C8-632AXSP16	79.9	124.9	95.4	107.3	206.5	79.9	123.8	95.1	106.7	204.2	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550C9-425AXSP16	69.1	109.4	83.1	93.9	183.3	69.3	108.6	82.9	93.4	181.7	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C9-432AXSP16	63.4	101.3	76.6	86.7	171	63.5	100.7	76.4	86.3	169.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550C9-525AXSP16	76.8	120.4	91.9	103.3	199.4	76.8	119.6	91.5	102.8	197.5	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550C9-532AXSP16	71.4	113	85.8	96.7	188.7	71.5	112.2	85.6	96.3	187	180	18.3	2"	144</					

EAW-VD15S1ZK550K9-632AXSP16	76.3	119.1	91	102.3	196.7	76.4	118.2	90.7	101.9	194.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550R3-425AXSP16	68.3	107.9	82.1	92.7	180.8	68.4	107.3	81.9	92.3	179.3	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550R3-432AXSP16	62.9	100.4	76	85.9	169.2	63	99.9	75.8	85.6	167.9	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK550R3-525AXSP16	75.6	118.3	90.2	101.6	195.9	75.6	117.5	90.1	101.2	194	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550R3-532AXSP16	70.5	111.4	84.6	95.4	186.2	70.6	110.7	84.5	95.1	184.4	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK550R3-625AXSP16	83	128.2	98.6	110.5	210	83.1	127.4	98.3	109.8	207.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK550R3-632AXSP16	78.5	122.6	93.7	105.3	202.8	78.7	121.8	93.4	104.8	200.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C2-425AXSP16	74.5	117.8	89.5	101.1	197.9	74.5	117.1	89.4	100.7	196.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C2-432AXSP16	68.3	109	82.6	93.3	184.4	68.5	108.5	82.4	93.1	182.8	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C3-525AXSP16	82.6	129.5	98.9	111.3	215.3	82.8	128.9	98.7	110.8	213.3	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C2-532AXSP16	76.8	121.8	92.3	104.2	203.6	77	121	92.3	103.9	201.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C2-625AXSP16	91.1	141.2	108.3	121.5	231.7	91.3	140.3	108.1	121	229.6	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C3-632AXSP16	85.9	134.5	102.7	115.6	222.9	86.1	133.8	102.5	115.1	220.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C3-425AXSP16	74.5	117.8	89.5	101.1	197.9	74.5	117.1	89.4	100.7	196.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C3-432AXSP16	68.3	109	82.6	93.3	184.4	68.5	108.5	82.4	93.1	182.8	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C3-525AXSP16	82.6	129.5	98.9	111.3	215.3	82.8	128.9	98.7	110.8	213.3	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C3-532AXSP16	76.8	121.8	92.3	104.2	203.6	77	121	92.3	103.9	201.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C3-625AXSP16	91.1	141.2	108.3	121.5	231.7	91.3	140.3	108.1	121	229.6	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C3-632AXSP16	85.9	134.5	102.7	115.6	222.9	86.1	133.8	102.5	115.1	220.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C4-425AXSP16	74.5	117.8	89.5	101.1	197.9	74.5	117.1	89.4	100.7	196.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C4-432AXSP16	68.3	109	82.6	93.3	184.4	68.5	108.5	82.4	93.1	182.8	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C4-525AXSP16	82.6	129.5	98.9	111.3	215.3	82.8	128.9	98.7	110.8	213.3	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C4-532AXSP16	76.8	121.8	92.3	104.2	203.6	77	121	92.3	103.9	201.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C5-625AXSP16	91.1	141.2	108.3	121.5	231.7	91.3	140.3	108.1	121	229.6	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C5-632AXSP16	85.9	134.5	102.7	115.6	222.9	86.1	133.8	102.5	115.1	220.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C5-632AXSP16	85.9	134.5	102.7	115.6	222.9	86.1	133.8	102.5	115.1	220.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C8-425AXSP16	74.5	117.8	89.5	101.1	197.9	74.5	117.1	89.4	100.7	196.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C8-432AXSP16	68.3	109	82.6	93.3	184.4	68.5	108.5	82.4	93.1	182.8	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C8-525AXSP16	82.6	129.5	98.9	111.3	215.3	82.8	128.9	98.7	110.8	213.3	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C8-532AXSP16	76.8	121.8	92.3	104.2	203.6	77	121	92.3	103.9	201.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C8-625AXSP16	91.1	141.2	108.3	121.5	231.7	91.3	140.3	108.1	121	229.6	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C8-632AXSP16	85.9	134.5	102.7	115.6	222.9	86.1	133.8	102.5	115.1	220.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C9-425AXSP16	74.5	117.8	89.5	101.1	197.9	74.5	117.1	89.4	100.7	196.1	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C9-432AXSP16	68.3	109	82.6	93.3	184.4	68.5	108.5	82.4	93.1	182.8	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750C9-525AXSP16	82.6	129.5	98.9	111.3	215.3	82.8	128.9	98.7	110.8	213.3	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C9-532AXSP16	76.8	121.8	92.3	104.2	203.6	77	121	92.3	103.9	201.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750C9-625AXSP16	91.1	141.2	108.3	121.5	231.7	91.3	140.3	108.1	121	229.6	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750C9-632AXSP16	85.9	134.5	102.7	115.6	222.9	86.1	133.8	102.5	115.1	220.7	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K2-425AXSP16	72	113.8	86.6	97.8	191.1	72.2	113.4	86.5	97.4	189.6	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K2-432AXSP16	66.2	105.8	80.1	90.6	178.6	66.4	105.3	79.9	90.2	177.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K2-525AXSP16	79.8	125	95.5	107.4	207.5	79.9	124.3	95.2	106.9	205.6	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K2-532AXSP16	74.3	117.6	89.3	100.8	196.7	74.4	116.9	89.1	100.3	194.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K2-625AXSP16	87.8	135.9	104.3	117	222.7	87.9	134.9	103.9	116.3	220.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K2-632AXSP16	82.9	129.7	99.1	111.4	214.6	83.1	129	98.9	111	212.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K3-425AXSP16	72	113.8	86.6	97.8	191.1	72.2	113.4	86.5	97.4	189.6	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K3-432AXSP16	66.2	105.8	80.1	90.6	178.6	66.4	105.3	79.9	90.2	177.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K3-525AXSP16	79.8	125	95.5	107.4	207.5	79.9	124.3	95.2	106.9	205.6	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K3-532AXSP16	74.3	117.6	89.3	100.8	196.7	74.4	116.9	89.1	100.3	194.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K3-625AXSP16	87.8	135.9	104.3	117	222.7	87.9	134.9	103.9	116.3	220.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K3-632AXSP16	82.9	129.7	99.1	111.4	214.6	83.1	129	98.9	111	212.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K4-425AXSP16	72	113.8	86.6	97.8	191.1	72.2	113.4	86.5	97.4	189.6	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K4-432AXSP16	66.2	105.8	80.1	90.6	178.6	66.4	105.3	79.9	90.2	177.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K4-525AXSP16	79.8	125	95.5	107.4	207.5	79.9	124.3	95.2	106.9	205.6	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K4-532AXSP16	74.3	117.6	89.3	100.8	196.7	74.4	116.9	89.1	100.3	194.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K4-625AXSP16	87.8	135.9	104.3	117	222.7	87.9	134.9	103.9	116.3	220.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K4-632AXSP16	82.9	129.7	99.1	111.4	214.6	83.1	129	98.9	111	212.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K5-425AXSP16	72	113.8	86.6	97.8	191.1	72.2	113.4	86.5	97.4	189.6	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K5-432AXSP16	66.2	105.8	80.1	90.6	178.6	66.4	105.3	79.9	90.2	177.4	146	17.2	2"	117	13.8	1-1/2"	176	24.1	2"
EAW-VD15S1ZK750K5-525AXSP16	79.8	125	95.5	107.4	207.5	79.9	124.3	95.2	106.9	205.6	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K5-532AXSP16	74.3	117.6	89.3	100.8	196.7	74.4	116.9	89.1	100.3	194.9	180	18.3	2"	144	12	2"	216	25.7	2"
EAW-VD15S1ZK750K5-625AXSP16	87.8	135.9	104.3	117	222.7	87.9	134.9	103.9	116.3	220.4	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K5-632AXSP16	82.9	129.7	99.1	111.4	214.6	83.1	129	98.9	111	212.8	225	20	2"	180	13.2	2"	270	22.5	3"
EAW-VD15S1ZK750K8-425AXSP16	72	113.8	86.6	97.8	191.1	72.2	113.4	86.5	97.4	189.6	146	17.2	2"	117	13.8	1-1/2"	176		

EAW-VD15S2PB370C5-625AXSP16	131.4	197.2	153.5	170.8	-	130.9	196	152.8	170	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370C5-632AXSP16	125.4	190.2	147.3	164.3	-	125	188.8	146.4	163.3	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370C8-425AXSP12	106.7	166	126.9	142.5	-	106.7	165	126.6	142.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370C8-432AXSP12	98.7	154.3	117.9	132.6	-	98.7	153.6	117.4	132	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370C8-525AXSP12	117.6	180.7	139.2	155.8	298.3	117.6	179.8	138.8	155.3	296	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370C8-532AXSP12	110.2	170.9	131	147.1	284.3	110.2	170.1	130.6	146.6	282	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370C8-625AXSP16	131.4	197.2	153.5	170.8	-	130.9	196	152.8	170	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370C8-632AXSP16	125.4	190.2	147.3	164.3	-	125	188.8	146.4	163.3	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K2-425AXSP12	102.9	159.5	122.4	137.3	-	102.7	158.7	122	136.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K2-432AXSP12	95.3	148.8	113.7	127.8	-	95.2	148.2	113.4	127.4	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K2-525AXSP12	113.1	173.7	133.8	149.7	286.1	113	172.8	133.3	149.1	283.8	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K2-532AXSP12	106.1	164.5	126.3	141.5	273.4	106.1	163.7	125.9	141	271.1	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K2-625AXSP16	126.5	189.6	147.7	164.2	-	126	188.3	146.9	163.2	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K2-632AXSP16	120.5	182.6	141.5	157.8	-	120.1	181.2	140.9	156.9	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K4-425AXSP12	102.9	159.5	122.4	137.3	-	102.7	158.7	122	136.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K4-432AXSP12	95.3	148.8	113.7	127.8	-	95.2	148.2	113.4	127.4	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K4-525AXSP12	113.1	173.7	133.8	149.7	286.1	113	172.8	133.3	149.1	283.8	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K4-532AXSP12	106.1	164.5	126.3	141.5	273.4	106.1	163.7	125.9	141	271.1	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K4-625AXSP16	126.5	189.6	147.7	164.2	-	126	188.3	146.9	163.2	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K4-632AXSP16	120.5	182.6	141.5	157.8	-	120.1	181.2	140.9	156.9	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K5-425AXSP12	102.9	159.5	122.4	137.3	-	102.7	158.7	122	136.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K5-432AXSP12	95.3	148.8	113.7	127.8	-	95.2	148.2	113.4	127.4	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K5-525AXSP12	113.1	173.7	133.8	149.7	286.1	113	172.8	133.3	149.1	283.8	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K5-532AXSP12	106.1	164.5	126.3	141.5	273.4	106.1	163.7	125.9	141	271.1	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K5-625AXSP16	126.5	189.6	147.7	164.2	-	126	188.3	146.9	163.2	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K5-632AXSP16	120.5	182.6	141.5	157.8	-	120.1	181.2	140.9	156.9	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K8-425AXSP12	102.9	159.5	122.4	137.3	-	102.7	158.7	122	136.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K8-432AXSP12	95.3	148.8	113.7	127.8	-	95.2	148.2	113.4	127.4	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB370K8-525AXSP12	113.1	173.7	133.8	149.7	286.1	113	172.8	133.3	149.1	283.8	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K8-532AXSP12	106.1	164.5	126.3	141.5	273.4	106.1	163.7	125.9	141	271.1	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB370K8-625AXSP16	126.5	189.6	147.7	164.2	-	126	188.3	146.9	163.2	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB370K8-632AXSP16	120.5	182.6	141.5	157.8	-	120.1	181.2	140.9	156.9	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400B3-425AXSP12	103.7	161.1	123.4	138.7	-	103.8	160.4	123	138	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400B3-432AXSP12	96.2	150.4	114.8	129.1	-	96.2	149.8	114.6	128.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400B3-525AXSP12	113.7	174.7	134.6	150.8	288.2	113.8	174	134.4	150.1	286.2	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400B3-532AXSP16	109.5	168.1	129.4	144.9	-	109.3	167.1	129	144.2	-	135	29	1-1/2"	108	19.1	1-1/2"	162	36.4	2"
EAW-VD15S2PB400B3-625AXSP16	126.6	189.9	147.9	164.6	-	126.4	188.9	147.4	163.8	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400B3-632AXSP16	121.3	183.9	142.5	158.9	-	121	182.7	141.8	158.1	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400C3-425AXSP12	106.7	166	126.9	142.5	-	106.7	165	126.6	142.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400C3-432AXSP12	98.7	154.3	117.9	132.6	-	98.7	153.6	117.4	132	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400C3-525AXSP12	117.6	180.7	139.2	155.8	298.3	117.6	179.8	138.8	155.3	296	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400C3-532AXSP12	110.2	170.9	131	147.1	284.3	110.2	170.1	130.6	146.6	282	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400C3-625AXSP16	131.4	197.2	153.5	170.8	-	130.9	196	152.8	170	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400C3-632AXSP16	125.4	190.2	147.3	164.3	-	125	188.8	146.4	163.3	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400C9-425AXSP12	106.7	166	126.9	142.5	-	106.7	165	126.6	142.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400C9-432AXSP12	98.7	154.3	117.9	132.6	-	98.7	153.6	117.4	132	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400C9-525AXSP12	117.6	180.7	139.2	155.8	298.3	117.6	179.8	138.8	155.3	296	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400C9-532AXSP12	110.2	170.9	131	147.1	284.3	110.2	170.1	130.6	146.6	282	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400C9-625AXSP16	131.4	197.2	153.5	170.8	-	130.9	196	152.8	170	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400C9-632AXSP16	125.4	190.2	147.3	164.3	-	125	188.8	146.4	163.3	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400K3-425AXSP12	102.9	159.5	122.4	137.3	-	102.7	158.7	122	136.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400K3-432AXSP12	95.3	148.8	113.7	127.8	-	95.2	148.2	113.4	127.4	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400K3-525AXSP12	113.1	173.7	133.8	149.7	286.1	113	172.8	133.3	149.1	283.8	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400K3-532AXSP12	106.1	164.5	126.3	141.5	273.4	106.1	163.7	125.9	141	271.1	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400K3-625AXSP16	126.5	189.6	147.7	164.2	-	126	188.3	146.9	163.2	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400K3-632AXSP16	120.5	182.6	141.5	157.8	-	120.1	181.2	140.9	156.9	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400K9-425AXSP12	102.9	159.5	122.4	137.3	-	102.7	158.7	122	136.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400K9-525AXSP12	95.3	148.8	113.7	127.8	-	95.2	148.2	113.4	127.4	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400K9-532AXSP12	113.1	173.7	133.8	149.7	286.1	113	172.8	133.3	149.1	283.8	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB400K9-625AXSP16	126.5	189.6	147.7	164.2	-	126	188.3	146.9	163.2	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400K9-632AXSP16	120.5	182.6	141.5	157.8	-	120.1	181.2	140.9	156.9	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB400R3-425AXSP12	104.6	162.3	124.2	139.7	-	104.5	161.6	123.9	139	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400R3-432AXSP12	96.9	151.3	115.5	130.1	-	96.9	150.7	115.3	129.6	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB400R3-525AXSP12	114.9	176.5	136	152.1	291	114.9	175.7	135.5											

EAW-VD15S2PB8550C8-532AXSP12	122.8	190.9	146.2	164.4	-	123	190.2	145.9	163.8	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550C8-625AXSP12	144.7	220.3	170.4	190.1	360.3	144.7	219.1	169.9	189.6	357.9	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550C8-632AXSP12	137	211.1	162.4	181.8	348.1	137.1	209.9	162	181.3	345.7	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550C9-425AXSP12	118.8	185.5	141.7	159.4	-	118.9	184.6	141.5	158.8	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550C9-432AXSP12	109.5	171.8	131	147.4	-	109.5	171.2	130.7	147.2	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550C9-525AXSP12	131.6	202.8	155.9	174.8	-	131.7	202.1	155.6	174.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550C9-532AXSP12	122.8	190.9	146.2	164.4	-	123	190.2	145.9	163.8	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550C9-625AXSP12	144.7	220.3	170.4	190.1	360.3	144.7	219.1	169.9	189.6	357.9	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550C9-632AXSP12	137	211.1	162.4	181.8	348.1	137.1	209.9	162	181.3	345.7	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K2-425AXSP12	113.7	177	135.5	152.2	-	113.7	176.4	135.3	151.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K2-432AXSP12	105.1	164.7	125.5	141.3	-	105.1	163.9	125.3	141.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K2-525AXSP12	125.5	192.9	148.6	166.4	-	125.3	192.2	148.2	165.7	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K2-532AXSP12	117.4	182.4	139.7	157	-	117.6	181.7	139.4	156.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K2-625AXSP12	137.5	209	161.8	180.5	341.3	137.4	207.8	161.3	179.9	338.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K2-632AXSP16	133.5	203	157.1	175.4	-	133.2	201.8	156.4	174.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB8550K3-425AXSP12	113.7	177	135.5	152.2	-	113.7	176.4	135.3	151.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K3-432AXSP12	105.1	164.7	125.5	141.3	-	105.1	163.9	125.3	141.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K3-525AXSP12	125.5	192.9	148.6	166.4	-	125.3	192.2	148.2	165.7	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K3-532AXSP12	117.4	182.4	139.7	157	-	117.6	181.7	139.4	156.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K3-625AXSP12	137.5	209	161.8	180.5	341.3	137.4	207.8	161.3	179.9	338.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K3-632AXSP16	133.5	203	157.1	175.4	-	133.2	201.8	156.4	174.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB8550K4-425AXSP12	113.7	177	135.5	152.2	-	113.7	176.4	135.3	151.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K4-432AXSP12	105.1	164.7	125.5	141.3	-	105.1	163.9	125.3	141.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K4-525AXSP12	125.5	192.9	148.6	166.4	-	125.3	192.2	148.2	165.7	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K4-532AXSP12	117.4	182.4	139.7	157	-	117.6	181.7	139.4	156.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K4-625AXSP12	137.5	209	161.8	180.5	341.3	137.4	207.8	161.3	179.9	338.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K4-632AXSP16	133.5	203	157.1	175.4	-	133.2	201.8	156.4	174.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB8550K5-425AXSP12	113.7	177	135.5	152.2	-	113.7	176.4	135.3	151.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K5-432AXSP12	105.1	164.7	125.5	141.3	-	105.1	163.9	125.3	141.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K5-525AXSP12	125.5	192.9	148.6	166.4	-	125.3	192.2	148.2	165.7	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K5-532AXSP12	117.4	182.4	139.7	157	-	117.6	181.7	139.4	156.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K5-625AXSP12	137.5	209	161.8	180.5	341.3	137.4	207.8	161.3	179.9	338.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K5-632AXSP16	133.5	203	157.1	175.4	-	133.2	201.8	156.4	174.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB8550K8-425AXSP12	113.7	177	135.5	152.2	-	113.7	176.4	135.3	151.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K8-432AXSP12	105.1	164.7	125.5	141.3	-	105.1	163.9	125.3	141.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K8-525AXSP12	125.5	192.9	148.6	166.4	-	125.3	192.2	148.2	165.7	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K8-532AXSP12	117.4	182.4	139.7	157	-	117.6	181.7	139.4	156.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K8-625AXSP12	137.5	209	161.8	180.5	341.3	137.4	207.8	161.3	179.9	338.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K8-632AXSP16	133.5	203	157.1	175.4	-	133.2	201.8	156.4	174.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB8550K9-425AXSP12	113.7	177	135.5	152.2	-	113.7	176.4	135.3	151.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K9-432AXSP12	105.1	164.7	125.5	141.3	-	105.1	163.9	125.3	141.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550K9-525AXSP12	125.5	192.9	148.6	166.4	-	125.3	192.2	148.2	165.7	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K9-532AXSP12	117.4	182.4	139.7	157	-	117.6	181.7	139.4	156.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550K9-625AXSP12	137.5	209	161.8	180.5	341.3	137.4	207.8	161.3	179.9	338.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550K9-632AXSP16	133.5	203	157.1	175.4	-	133.2	201.8	156.4	174.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD15S2PB8550R3-425AXSP12	116.4	181.4	138.7	155.9	-	116.5	180.6	138.3	155.5	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550R3-432AXSP12	107.6	168.6	128.6	144.8	-	107.6	168.1	128.4	144.3	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8550R3-525AXSP12	128.4	197.7	152.1	170.4	-	128.3	197	151.8	169.8	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550R3-532AXSP12	120.1	186.8	142.9	160.5	-	120.4	185.9	142.7	160.2	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8550R3-625AXSP12	140.7	214	165.8	185.1	349.8	140.6	213.2	165.4	184.3	347.5	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8550R3-632AXSP12	133.7	205.4	158.5	177.3	339	133.8	204.6	158	176.5	336.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8750C2-425AXSP12	125.6	196.5	149.9	168.8	-	125.9	195.8	150	168.5	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8750C2-432AXSP12	115.9	182.2	138.8	156.4	-	116	181.9	138.6	156.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8750C2-525AXSP12	138.8	214.4	164.5	184.6	-	138.9	214	164.5	184.5	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8750C2-532AXSP12	129.8	202.1	154.6	173.8	-	130	201.7	154.3	173.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8750C2-625AXSP12	152.4	232.1	179.5	200.4	-	152.5	231.4	179.4	200	-	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8750C2-632AXSP12	144.6	222.9	171.5	192.1	368.2	144.9	222	171.3	191.6	366.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8750C3-425AXSP12	125.6	196.5	149.9	168.8	-	125.9	195.8	150	168.5	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8750C3-432AXSP12	115.9	182.2	138.8	156.4	-	116	181.9	138.6	156.1	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB8750C3-525AXSP12	138.8	214.4	164.5	184.6	-	138.9	214	164.5	184.5	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8750C3-532AXSP12	129.8	202.1	154.6	173.8	-	130	201.7	154.3	173.4	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB8750C3-625AXSP12	152.4	232.1	179.5	200.4	-	152.5	231.4	179.4	200	-	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8750C3-632AXSP12	144.6	222.9	171.5	192.1	368.2	144.9	222	171.3	191.6	366.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB8750C4-425AXSP12	125.6	196.5	149.9	168.8	-	125.9	195.8	150	168.5	-	146	20.1	2"	117					

EAW-VD15S2PB750K4-525AXSP12	134.2	207	159	178.3	-	134.2	206.5	158.9	178.1	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K4-532AXSP12	125.6	195.3	149.6	168.1	-	125.8	194.8	149.3	167.6	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K4-625AXSP12	147.2	224	173.4	193.5	366.9	147.5	223.6	173.2	193.4	365.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K4-632AXSP12	139.9	215.3	165.6	185.4	355.2	140.1	214.3	165.3	185	353.1	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K5-425AXSP12	121.6	189.8	145.1	163.2	-	121.9	189.5	144.8	162.9	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750K5-432AXSP12	112.4	176.5	134.4	151.4	-	112.5	176	134.3	151.2	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750K5-525AXSP12	134.2	207	159	178.3	-	134.2	206.5	158.9	178.1	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K5-532AXSP12	125.6	195.3	149.6	168.1	-	125.8	194.8	149.3	167.6	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K5-625AXSP12	147.2	224	173.4	193.5	366.9	147.5	223.6	173.2	193.4	365.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K5-632AXSP12	139.9	215.3	165.6	185.4	355.2	140.1	214.3	165.3	185	353.1	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K8-425AXSP12	121.6	189.8	145.1	163.2	-	121.9	189.5	144.8	162.9	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750K8-432AXSP12	112.4	176.5	134.4	151.4	-	112.5	176	134.3	151.2	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750K8-525AXSP12	134.2	207	159	178.3	-	134.2	206.5	158.9	178.1	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K8-532AXSP12	125.6	195.3	149.6	168.1	-	125.8	194.8	149.3	167.6	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K8-625AXSP12	147.2	224	173.4	193.5	366.9	147.5	223.6	173.2	193.4	365.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K8-632AXSP12	139.9	215.3	165.6	185.4	355.2	140.1	214.3	165.3	185	353.1	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K9-425AXSP12	121.6	189.8	145.1	163.2	-	121.9	189.5	144.8	162.9	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750K9-432AXSP12	112.4	176.5	134.4	151.4	-	112.5	176	134.3	151.2	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750K9-525AXSP12	134.2	207	159	178.3	-	134.2	206.5	158.9	178.1	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K9-532AXSP12	125.6	195.3	149.6	168.1	-	125.8	194.8	149.3	167.6	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750K9-625AXSP12	147.2	224	173.4	193.5	366.9	147.5	223.6	173.2	193.4	365.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750K9-632AXSP12	139.9	215.3	165.6	185.4	355.2	140.1	214.3	165.3	185	353.1	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750R3-425AXSP12	119	185.8	141.9	159.6	-	119.2	185.4	141.9	159.5	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750R3-432AXSP12	110.1	173.1	131.8	148.5	-	110.3	172.5	131.7	148.3	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD15S2PB750R3-525AXSP12	131.3	202.4	155.6	174.4	-	131.4	201.8	155.4	173.9	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750R3-532AXSP12	122.9	191.2	146.4	164.3	-	123.1	190.7	146.3	164.2	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD15S2PB750R3-625AXSP12	143.8	218.7	169.4	189	358	143.9	217.9	169.2	188.6	355.9	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PB750R3-632AXSP12	136.7	210.2	162	181.3	347.1	136.9	209.5	161.7	181	345	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD15S2PI370C2-425AXSP08	122.2	190.4	145.8	163.9	316.8	122.1	189	145.3	162.9	313.6	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI370C2-432AXSP12	115.4	178.1	136.7	153.6	-	114.7	176.7	135.9	152.3	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370C2-525AXSP12	138.1	209.2	162.2	180.8	-	137.2	207.4	161	179.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C2-532AXSP12	129.3	197.7	152.6	170.6	-	128.7	195.7	151.5	169.1	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C2-625AXSP12	151.6	226.4	176.8	196.3	364.8	150.5	224.1	175.1	194.5	360.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C2-632AXSP12	144	217.1	168.8	188	353.4	143	215.1	167.4	186.2	349.3	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C4-425AXSP08	122.2	190.4	145.8	163.9	316.8	122.1	189	145.3	162.9	313.6	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI370C4-432AXSP12	115.4	178.1	136.7	153.6	-	114.7	176.7	135.9	152.3	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370C4-525AXSP12	138.1	209.2	162.2	180.8	-	137.2	207.4	161	179.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C4-532AXSP12	129.3	197.7	152.6	170.6	-	128.7	195.7	151.5	169.1	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C4-625AXSP12	151.6	226.4	176.8	196.3	364.8	150.5	224.1	175.1	194.5	360.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C4-632AXSP12	144	217.1	168.8	188	353.4	143	215.1	167.4	186.2	349.3	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C5-425AXSP08	122.2	190.4	145.8	163.9	316.8	122.1	189	145.3	162.9	313.6	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI370C5-432AXSP12	115.4	178.1	136.7	153.6	-	114.7	176.7	135.9	152.3	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370C5-525AXSP12	138.1	209.2	162.2	180.8	-	137.2	207.4	161	179.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C5-532AXSP12	129.3	197.7	152.6	170.6	-	128.7	195.7	151.5	169.1	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C5-625AXSP12	151.6	226.4	176.8	196.3	364.8	150.5	224.1	175.1	194.5	360.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C5-632AXSP12	144	217.1	168.8	188	353.4	143	215.1	167.4	186.2	349.3	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C8-425AXSP08	122.2	190.4	145.8	163.9	316.8	122.1	189	145.3	162.9	313.6	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI370C8-432AXSP12	115.4	178.1	136.7	153.6	-	114.7	176.7	135.9	152.3	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370C8-525AXSP12	138.1	209.2	162.2	180.8	-	137.2	207.4	161	179.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C8-532AXSP12	129.3	197.7	152.6	170.6	-	128.7	195.7	151.5	169.1	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370C8-625AXSP12	151.6	226.4	176.8	196.3	364.8	150.5	224.1	175.1	194.5	360.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370C8-632AXSP12	144	217.1	168.8	188	353.4	143	215.1	167.4	186.2	349.3	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370K2-425AXSP12	120.2	184.3	141.9	158.8	-	119.7	182.5	141	157.7	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370K2-432AXSP12	111.3	172.1	132	148	-	110.8	170.5	131.2	147	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370K2-525AXSP12	132.7	200.6	155.6	173.5	-	131.9	198.9	154.5	172.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370K2-532AXSP12	124.6	190	146.8	164	-	123.8	188.3	145.7	162.8	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370K2-625AXSP12	145.2	216.7	169.4	188	348.7	144.4	214.5	167.8	186.3	344.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370K2-632AXSP12	138.2	208.4	162	180.4	338.2	137.4	206.2	160.7	178.7	334.3	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370K4-425AXSP12	120.2	184.3	141.9	158.8	-	119.7	182.5	141	157.7	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370K4-432AXSP12	111.3	172.1	132	148	-	110.8	170.5	131.2	147	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2PI370K4-525AXSP12	132.7	200.6	155.6	173.5	-	131.9	198.9	154.5	172.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370K4-532AXSP12	124.6	190	146.8	164	-	123.8	188.3	145.7	162.8	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PI370K4-625AXSP12	145.2	216.7	169.4	188	348.7	144.4	214.5	167.8	186.3	344.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI370K4-632AXSP12	138.2	208.4	162	180.4	338.2	137.4	206.2	160.7	178.7	334.3	225	27.9	2"	180	18.4	2"	270</		

EAW-VD15S2P1400K9-432AXSP12	111.3	172.1	132	148	-	110.8	170.5	131.2	147	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2P1400K9-525AXSP12	132.7	200.6	155.6	173.5	-	131.9	198.9	154.5	172.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1400K9-532AXSP12	124.6	190	146.8	164	-	123.8	188.3	145.7	162.8	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1400K9-625AXSP12	145.2	216.7	169.4	188	348.7	144.4	214.5	167.8	186.3	344.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1400K9-632AXSP12	138.2	208.4	162	180.4	338.2	137.4	206.2	160.7	178.7	334.3	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1400R3-425AXSP08	119.9	187	143.2	160.8	310.6	120	185.6	142.7	160	307.7	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1400R3-432AXSP12	113.6	175.4	134.7	151	-	113.1	174.1	134	150.1	-	146	25.3	2"	117	19	1-1/2"	176	35.5	2"
EAW-VD15S2P1400R3-525AXSP12	135.3	204.9	158.9	177.2	-	134.5	202.9	157.8	175.7	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1400R3-532AXSP12	127	193.8	149.7	167.3	-	126.3	192.3	148.7	166.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1400R3-625AXSP12	148.2	221.2	172.5	191.8	355.9	147.2	219	171.2	190.1	351.7	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1400R3-632AXSP12	141.1	212.6	165.3	184.2	345.5	140.2	210.7	163.9	182.5	341.6	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550B3-425AXSP08	131.2	204.6	156.5	176.1	341.3	131.2	203.4	156	175.1	338.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550B3-432AXSP08	121.1	190.6	145.2	163.6	319.6	121	189.3	144.8	162.8	316.8	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550B3-525AXSP08	145.8	224.9	173.2	193.9	370.3	145.6	223.5	172.4	193	367	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550B3-532AXSP12	138.6	212.3	163.7	183.2	-	138	210.4	162.5	181.8	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550B3-625AXSP12	162.1	242.8	189.3	210.6	-	161.5	240.8	187.9	209	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550B3-632AXSP12	154.4	233.3	181	201.8	-	153.6	231.2	179.9	200.2	376.4	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C2-425AXSP08	137.2	214	163.8	184	357.6	137.1	212.7	163.1	183.2	354.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C2-432AXSP08	126.1	198.7	151.4	170.5	334	126.3	197.4	151	169.9	330.9	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C2-525AXSP08	153.3	237	182.2	204.1	390.6	153.3	235.1	181.6	203	386.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550C2-532AXSP12	144.9	222.4	171.2	191.7	-	144.1	220.6	170.1	190.4	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550C2-625AXSP12	171.4	257.4	200.4	223.1	-	170.5	254.9	198.7	221.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C2-632AXSP12	162.2	245.8	190.5	212.5	-	161.2	243.4	189.1	210.9	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C3-425AXSP08	137.2	214	163.8	184	357.6	137.1	212.7	163.1	183.2	354.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C3-432AXSP08	126.1	198.7	151.4	170.5	334	126.3	197.4	151	169.9	330.9	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C3-525AXSP08	153.3	237	182.2	204.1	390.6	153.3	235.1	181.6	203	386.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550C3-532AXSP12	144.9	222.4	171.2	191.7	-	144.1	220.6	170.1	190.4	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550C3-625AXSP12	171.4	257.4	200.4	223.1	-	170.5	254.9	198.7	221.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C3-632AXSP12	162.2	245.8	190.5	212.5	-	161.2	243.4	189.1	210.9	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C4-425AXSP08	137.2	214	163.8	184	357.6	137.1	212.7	163.1	183.2	354.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C4-432AXSP08	126.1	198.7	151.4	170.5	334	126.3	197.4	151	169.9	330.9	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C4-525AXSP08	153.3	237	182.2	204.1	390.6	153.3	235.1	181.6	203	386.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550C4-532AXSP12	144.9	222.4	171.2	191.7	-	144.1	220.6	170.1	190.4	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550C4-625AXSP12	171.4	257.4	200.4	223.1	-	170.5	254.9	198.7	221.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C4-632AXSP12	162.2	245.8	190.5	212.5	-	161.2	243.4	189.1	210.9	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C5-425AXSP08	137.2	214	163.8	184	357.6	137.1	212.7	163.1	183.2	354.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C5-432AXSP08	126.1	198.7	151.4	170.5	334	126.3	197.4	151	169.9	330.9	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C5-525AXSP08	153.3	237	182.2	204.1	390.6	153.3	235.1	181.6	203	386.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550C5-532AXSP12	144.9	222.4	171.2	191.7	-	144.1	220.6	170.1	190.4	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550C5-625AXSP12	171.4	257.4	200.4	223.1	-	170.5	254.9	198.7	221.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C5-632AXSP12	162.2	245.8	190.5	212.5	-	161.2	243.4	189.1	210.9	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C8-425AXSP08	137.2	214	163.8	184	357.6	137.1	212.7	163.1	183.2	354.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C8-432AXSP08	126.1	198.7	151.4	170.5	334	126.3	197.4	151	169.9	330.9	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C8-525AXSP08	153.3	237	182.2	204.1	390.6	153.3	235.1	181.6	203	386.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550C8-532AXSP12	144.9	222.4	171.2	191.7	-	144.1	220.6	170.1	190.4	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550C8-625AXSP12	171.4	257.4	200.4	223.1	-	170.5	254.9	198.7	221.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C8-632AXSP12	162.2	245.8	190.5	212.5	-	161.2	243.4	189.1	210.9	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C9-425AXSP08	137.2	214	163.8	184	357.6	137.1	212.7	163.1	183.2	354.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C9-432AXSP08	126.1	198.7	151.4	170.5	334	126.3	197.4	151	169.9	330.9	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550C9-525AXSP08	153.3	237	182.2	204.1	390.6	153.3	235.1	181.6	203	386.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550C9-532AXSP12	144.9	222.4	171.2	191.7	-	144.1	220.6	170.1	190.4	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550C9-625AXSP12	171.4	257.4	200.4	223.1	-	170.5	254.9	198.7	221.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550C9-632AXSP12	162.2	245.8	190.5	212.5	-	161.2	243.4	189.1	210.9	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550K2-425AXSP08	131.4	204.9	157.1	176.4	341.9	131.4	203.8	156.5	175.6	338.8	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550K2-432AXSP08	121.5	190.9	145.7	163.9	320.3	121.4	190	145	163.1	318	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550K2-525AXSP08	146.3	225.7	173.8	194.6	371.7	146.1	224.3	173	193.6	368.3	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550K2-532AXSP12	138.8	212.7	164	183.5	-	138.2	211.1	163	182.1	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550K2-625AXSP12	163.1	244.3	190.5	211.9	-	162.1	242.1	188.9	210.2	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550K2-632AXSP12	155	234.2	181.7	202.5	-	154	232.2	180.4	200.8	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2P1550K3-425AXSP08	131.4	204.9	157.1	176.4	341.9	131.4	203.8	156.5	175.6	338.8	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550K3-432AXSP08	121.5	190.9	145.7	163.9	320.3	121.4	190	145	163.1	318	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2P1550K3-525AXSP08	146.3	225.7	173.8	194.6	371.7	146.1	224.3	173	193.6	368.3	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2P1550K3-532AXSP12	138.8	212.7	164	183.5	-	138.2	211.1	163	182.1	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2P1550K3-625AXSP12	163.1	244.3	190.5	211.9	-	162.1	242.1	188.9	210.2										

EAW-VD15S2PI750C3-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C3-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C3-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C3-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C3-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C3-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C4-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C4-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C4-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C4-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C4-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C4-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C5-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C5-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C5-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C5-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C5-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C5-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C8-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C8-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C8-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C8-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C8-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C8-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C9-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C9-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750C9-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C9-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750C9-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750C9-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K2-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K2-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K2-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K2-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K2-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K2-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K3-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K3-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K3-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K3-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K3-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K3-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K4-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K4-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K4-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K4-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K4-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K4-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K5-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K5-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K5-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K5-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K5-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K5-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K8-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K8-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K8-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K8-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K8-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K8-632AXSP12	173.4	263.4	204	227.7	-	172.6	261.3	202.6	226.1	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD15S2PI750K9-425AXSP08	147.2	229.7	175.5	197.5	-	147.1	228.7	175.1	196.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K9-432AXSP08	135.3	213	162.4	182.7	359.1	135.4	211.8	161.8	182.3	356.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD15S2PI750K9-525AXSP08	164.1	254.1	195.2	218.8	420.1	164.1	252.4	194.6	217.7	416.8	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K9-532AXSP08	153.2	239.2	183	205.5	398.3	153.2	237.9	182.5	204.8	395	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD15S2PI750K9-625AXSP12	183	275.4	214.4	238.7	-	182.4	273.6	213	237.1	-	225	27							

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S2PK370K2-632AXSP16	128	193	149.9	167	-	127.4	191.4	149	165.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK370K4-425AXSP12	109.3	168.9	129.5	145.4	-	109	167.6	128.9	144.4	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK370K4-432AXSP12	101.1	157.4	120.3	135.4	-	100.9	156.4	119.9	134.5	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK370K4-525AXSP12	120.4	183.8	141.9	158.7	-	120.1	182.7	141.2	157.9	299.3	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK370K4-532AXSP12	112.9	173.9	133.8	150	287.9	112.7	172.7	133.1	149.2	285.5	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK370K4-625AXSP12	131.6	198.3	154.4	171.7	321	131.2	196.7	153.5	170.6	318.2	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK370K4-632AXSP16	128	193	149.9	167	-	127.4	191.4	149	165.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK370K5-425AXSP12	109.3	168.9	129.5	145.4	-	109	167.6	128.9	144.4	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK370K5-432AXSP12	101.1	157.4	120.3	135.4	-	100.9	156.4	119.9	134.5	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK370K5-525AXSP12	120.4	183.8	141.9	158.7	-	120.1	182.7	141.2	157.9	299.3	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK370K5-532AXSP12	112.9	173.9	133.8	150	287.9	112.7	172.7	133.1	149.2	285.5	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK370K5-625AXSP12	131.6	198.3	154.4	171.7	321	131.2	196.7	153.5	170.6	318.2	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK370K5-632AXSP16	128	193	149.9	167	-	127.4	191.4	149	165.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK370K8-425AXSP12	109.3	168.9	129.5	145.4	-	109	167.6	128.9	144.4	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK370K8-432AXSP12	101.1	157.4	120.3	135.4	-	100.9	156.4	119.9	134.5	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK370K8-525AXSP12	120.4	183.8	141.9	158.7	-	120.1	182.7	141.2	157.9	299.3	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK370K8-532AXSP12	112.9	173.9	133.8	150	287.9	112.7	172.7	133.1	149.2	285.5	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK370K8-625AXSP12	131.6	198.3	154.4	171.7	321	131.2	196.7	153.5	170.6	318.2	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK370K8-632AXSP16	128	193	149.9	167	-	127.4	191.4	149	165.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK400B3-425AXSP12	110.5	170.8	131.1	147	-	110.3	169.6	130.6	146.2	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400B3-432AXSP12	102.3	159.4	121.8	137.1	-	102.2	158.5	121.4	136.3	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400B3-525AXSP12	121.6	185.7	143.3	160.3	-	121.4	184.3	142.7	159.3	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400B3-532AXSP12	114.2	176	135.4	151.6	291.1	113.9	174.7	134.8	150.9	288.9	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400B3-625AXSP12	132.4	199.8	155.3	173	323.4	132.1	198.4	154.6	172	320.5	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400B3-632AXSP16	129.3	194.9	151.3	168.7	-	128.5	193.4	150.3	167.5	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK400C3-425AXSP12	113.4	175.5	134.6	151	-	113.1	174.2	134	150.2	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400C3-432AXSP12	104.8	163.2	124.8	140.5	-	104.6	162.2	124.3	139.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400C3-525AXSP12	125.4	191.4	147.8	165.3	-	124.9	190.2	147.1	164.3	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400C3-532AXSP12	117.3	181	139.1	155.8	299.7	117.1	179.8	138.4	155	297.2	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400C3-625AXSP12	137.2	206.9	160.9	179.1	335.5	136.8	205.3	160.1	178.1	332.6	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400C3-632AXSP12	130.4	198.8	153.9	171.8	325.6	130.1	197.5	153	170.9	322.6	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400C9-425AXSP12	113.4	175.5	134.6	151	-	113.1	174.2	134	150.2	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400C9-432AXSP12	104.8	163.2	124.8	140.5	-	104.6	162.2	124.3	139.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400C9-525AXSP12	125.4	191.4	147.8	165.3	-	124.9	190.2	147.1	164.3	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400C9-532AXSP12	117.3	181	139.1	155.8	299.7	117.1	179.8	138.4	155	297.2	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400C9-625AXSP12	137.2	206.9	160.9	179.1	335.5	136.8	205.3	160.1	178.1	332.6	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400C9-632AXSP12	130.4	198.8	153.9	171.8	325.6	130.1	197.5	153	170.9	322.6	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400K3-425AXSP12	109.3	168.9	129.5	145.4	-	109	167.6	128.9	144.4	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400K3-432AXSP12	101.1	157.4	120.3	135.4	-	100.9	156.4	119.9	134.5	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400K3-625AXSP12	120.4	183.8	141.9	158.7	-	120.1	182.7	141.2	157.9	299.3	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400K3-532AXSP12	112.9	173.9	133.8	150	287.9	112.7	172.7	133.1	149.2	285.5	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400K3-632AXSP12	131.6	198.3	154.4	171.7	321	131.2	196.7	153.5	170.6	318.2	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400K3-632AXSP16	128	193	149.9	167	-	127.4	191.4	149	165.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK400K9-425AXSP12	109.3	168.9	129.5	145.4	-	109	167.6	128.9	144.4	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400K9-432AXSP12	101.1	157.4	120.3	135.4	-	100.9	156.4	119.9	134.5	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400K9-525AXSP12	120.4	183.8	141.9	158.7	-	120.1	182.7	141.2	157.9	299.3	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400K9-532AXSP12	112.9	173.9	133.8	150	287.9	112.7	172.7	133.1	149.2	285.5	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400K9-625AXSP12	131.6	198.3	154.4	171.7	321	131.2	196.7	153.5	170.6	318.2	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400K9-632AXSP16	128	193	149.9	167	-	127.4	191.4	149	165.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK400R3-425AXSP12	111.2	172	132	148	-	110.9	170.9	131.4	147.3	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400R3-432AXSP12	103.1	160.3	122.7	137.8	-	102.9	159.4	122.3	137.3	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK400R3-625AXSP12	122.5	187.2	144.4	161.5	-	122.3	185.8	143.8	160.7	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400R3-532AXSP12	115	177.2	136.3	152.6	293.6	114.8	176.1	135.7	151.9	290.9	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK400R3-625AXSP12	133.8	201.7	157	174.6	327	133.5	200.4	156.2	173.7	323.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK400R3-632AXSP16	130.3	196.5	152.5	170	-	129.5	194.9	151.7	168.8	-	169	29.1	2"	135	22.3	1-1/2"	203	40.9	2"
EAW-VD15S2PK50B3-425AXSP12	120.8	187.3	143.5	161.1	-	120.6	186.1	143.1	160.3	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK50B3-432AXSP12	111.7	174.1	133.1	149.7	-	111.6	173.4	132.8	149	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK50B3-525AXSP12	133	203.9	157.2	175.9	-	133	202.6	156.7	175	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK50B3-532AXSP12	124.9	192.8	148	165.9	-	124.8	191.9	147.6	165.4	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK50B3-625AXSP12	145.6	219.9	170.8	190.2	357.4	145.3	218.6	170	189.3	354.6	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK50B3-632AXSP12	138.7	211.7	163.8	182.8	347.6	138.6	210.6	162.9	182	344.4	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK50C2-425AXSP12	126.5	196.7	150.7	169	-	126.5	195.4	149.9	168.3	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK50C2-432AXSP12	116.6	182.2	139.2	156.7	-	116.4	181.3	138.5	155.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK50C2-525AXSP12	140.4	215.7	165.9	185.8	-	140.2	214.2	165.3	1										

EAW-VD15S2PK550K2-625AXSP12	147	221.9	172.3	192.1	361.1	146.6	220.6	171.5	191	357.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K2-632AXSP12	139.5	213.3	164.7	184.1	349.8	139.3	211.8	164	183	346.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K3-425AXSP12	121.2	188	144.1	161.7	-	121	186.8	143.6	160.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K3-432AXSP12	111.9	174.6	133.4	150	-	111.8	173.8	133	149.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K3-525AXSP12	134	205.1	158.1	176.9	-	133.6	204	157.5	176.2	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K3-532AXSP12	125.4	193.8	148.8	166.8	-	125.3	192.7	148.2	166.1	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K3-625AXSP12	147	221.9	172.3	192.1	361.1	146.6	220.6	171.5	191	357.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K3-632AXSP12	139.5	213.3	164.7	184.1	349.8	139.3	211.8	164	183	346.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K4-425AXSP12	121.2	188	144.1	161.7	-	121	186.8	143.6	160.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K4-432AXSP12	111.9	174.6	133.4	150	-	111.8	173.8	133	149.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K4-525AXSP12	134	205.1	158.1	176.9	-	133.6	204	157.5	176.2	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K4-532AXSP12	125.4	193.8	148.8	166.8	-	125.3	192.7	148.2	166.1	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K4-625AXSP12	147	221.9	172.3	192.1	361.1	146.6	220.6	171.5	191	357.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K4-632AXSP12	139.5	213.3	164.7	184.1	349.8	139.3	211.8	164	183	346.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K5-425AXSP12	121.2	188	144.1	161.7	-	121	186.8	143.6	160.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K5-432AXSP12	111.9	174.6	133.4	150	-	111.8	173.8	133	149.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K5-525AXSP12	134	205.1	158.1	176.9	-	133.6	204	157.5	176.2	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K5-532AXSP12	125.4	193.8	148.8	166.8	-	125.3	192.7	148.2	166.1	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K5-625AXSP12	147	221.9	172.3	192.1	361.1	146.6	220.6	171.5	191	357.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K5-632AXSP12	139.5	213.3	164.7	184.1	349.8	139.3	211.8	164	183	346.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K8-425AXSP12	121.2	188	144.1	161.7	-	121	186.8	143.6	160.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K8-432AXSP12	111.9	174.6	133.4	150	-	111.8	173.8	133	149.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K8-525AXSP12	134	205.1	158.1	176.9	-	133.6	204	157.5	176.2	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K8-532AXSP12	125.4	193.8	148.8	166.8	-	125.3	192.7	148.2	166.1	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K8-625AXSP12	147	221.9	172.3	192.1	361.1	146.6	220.6	171.5	191	357.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K8-632AXSP12	139.5	213.3	164.7	184.1	349.8	139.3	211.8	164	183	346.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K9-425AXSP12	121.2	188	144.1	161.7	-	121	186.8	143.6	160.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K9-432AXSP12	111.9	174.6	133.4	150	-	111.8	173.8	133	149.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550K9-525AXSP12	134	205.1	158.1	176.9	-	133.6	204	157.5	176.2	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K9-532AXSP12	125.4	193.8	148.8	166.8	-	125.3	192.7	148.2	166.1	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550K9-625AXSP12	147	221.9	172.3	192.1	361.1	146.6	220.6	171.5	191	357.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550K9-632AXSP12	139.5	213.3	164.7	184.1	349.8	139.3	211.8	164	183	346.9	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550R3-425AXSP12	124.1	192.8	147.8	165.7	-	124	191.9	147.1	165.2	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550R3-432AXSP12	114.7	179.2	136.8	153.9	-	114.7	178.2	136.5	153.2	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK550R3-525AXSP12	137.1	210.5	162.1	181.4	-	137.1	209.2	161.5	180.5	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550R3-532AXSP12	128.5	198.6	152.5	171.1	-	128.5	197.6	152.1	170.2	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK550R3-625AXSP12	150.7	227.9	176.8	197	371.1	150.5	226.4	175.9	196.2	367.8	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK550R3-632AXSP12	143	218.5	168.9	188.8	359.1	142.9	217.3	168.2	187.8	356.2	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C2-425AXSP08	131.1	207.3	157.9	178	350	131.7	206.9	157.9	177.6	348	225	17.9	2"	180	11.7	2"	270	19.8	3"
EAW-VD15S2PK750C2-432AXSP12	123.9	194.1	148	166.6	-	123.8	193.1	147.7	166	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750C2-525AXSP12	148.9	229	176.1	197.4	-	148.8	227.9	175.7	196.6	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C2-532AXSP12	139.1	215.5	165.3	185.6	-	139	214.7	164.9	184.8	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C2-625AXSP12	163.7	248.6	192.5	214.8	-	163.7	247.3	192	214	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C2-632AXSP12	155.5	238	183.4	205.3	-	155.2	236.9	182.9	204.6	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C3-425AXSP08	131.1	207.3	157.9	178	350	131.7	206.9	157.9	177.6	348	225	17.9	2"	180	11.7	2"	270	19.8	3"
EAW-VD15S2PK750C3-432AXSP12	123.9	194.1	148	166.6	-	123.8	193.1	147.7	166	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750C3-525AXSP12	148.9	229	176.1	197.4	-	148.8	227.9	175.7	196.6	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C3-532AXSP12	139.1	215.5	165.3	185.6	-	139	214.7	164.9	184.8	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C3-625AXSP12	163.7	248.6	192.5	214.8	-	163.7	247.3	192	214	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C3-632AXSP12	155.5	238	183.4	205.3	-	155.2	236.9	182.9	204.6	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C4-425AXSP08	131.1	207.3	157.9	178	350	131.7	206.9	157.9	177.6	348	225	17.9	2"	180	11.7	2"	270	19.8	3"
EAW-VD15S2PK750C4-432AXSP12	123.9	194.1	148	166.6	-	123.8	193.1	147.7	166	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750C4-525AXSP12	148.9	229	176.1	197.4	-	148.8	227.9	175.7	196.6	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C4-532AXSP12	139.1	215.5	165.3	185.6	-	139	214.7	164.9	184.8	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C4-625AXSP12	163.7	248.6	192.5	214.8	-	163.7	247.3	192	214	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C4-632AXSP12	155.5	238	183.4	205.3	-	155.2	236.9	182.9	204.6	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C5-425AXSP08	131.1	207.3	157.9	178	350	131.7	206.9	157.9	177.6	348	225	17.9	2"	180	11.7	2"	270	19.8	3"
EAW-VD15S2PK750C5-432AXSP12	123.9	194.1	148	166.6	-	123.8	193.1	147.7	166	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750C5-525AXSP12	148.9	229	176.1	197.4	-	148.8	227.9	175.7	196.6	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C5-532AXSP12	139.1	215.5	165.3	185.6	-	139	214.7	164.9	184.8	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C5-625AXSP12	163.7	248.6	192.5	214.8	-	163.7	247.3	192	214	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C5-632AXSP12	155.5	238	183.4	205.3	-	155.2	236.9	182.9	204.6	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750C8-425AXSP08	131.1	207.3	157.9	178	350	131.7	206.9	157.9	177.6	348	225	17.9	2"	180	11.7	2"	270	19.8	3"
EAW-VD15S2PK750C8-432AXSP12	123.9	194.1	148	166.6	-	123.8	193.1	147.7	166	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750C8-525AXSP12	148.9	229	176.1	197.4	-	148.8	227.9	175.7	196.6	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750C8-532AXSP12	139.1	215.5																	

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S2PK750K8-532AXSP12	134.6	208.5	159.9	179.4	-	134.6	207.5	159.3	178.8	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750K8-625AXSP12	157.9	239.2	185.4	206.8	-	157.8	238.2	184.8	205.9	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750K8-632AXSP12	150.1	229.4	177	198	-	149.8	228.4	176.5	197.1	374.7	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750K9-425AXSP08	126.8	200.5	152.6	171.9	338	127.4	200.1	152.7	171.9	336.1	225	17.9	2"	180	11.7	2"	270	19.8	3"
EAW-VD15S2PK750K9-432AXSP12	120.1	188	143.5	161.5	-	120.1	187.1	142.9	160.9	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750K9-525AXSP12	143.7	220.8	170	190.4	-	143.6	219.9	169.6	189.6	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750K9-532AXSP12	134.6	208.5	159.9	179.4	-	134.6	207.5	159.3	178.8	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750K9-625AXSP12	157.9	239.2	185.4	206.8	-	157.8	238.2	184.8	205.9	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750K9-632AXSP12	150.1	229.4	177	198	-	149.8	228.4	176.5	197.1	374.7	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750R3-425AXSP12	127.6	198.1	151.7	170.4	-	127.4	197.1	151.2	169.8	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750R3-432AXSP12	117.8	184	140.5	158.2	-	117.7	183.4	140.1	157.6	-	146	21.9	2"	117	16.7	1-1/2"	176	30.7	2"
EAW-VD15S2PK750R3-525AXSP12	140.6	215.8	166.2	186.2	-	140.5	214.9	165.8	185.4	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750R3-532AXSP12	131.7	203.8	156.4	175.4	-	131.6	203	156.1	175	-	180	22.9	2"	144	15.1	2"	216	32.1	2"
EAW-VD15S2PK750R3-625AXSP12	154.3	233.6	181.1	202.1	-	154	232.2	180.6	201.1	-	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2PK750R3-632AXSP12	146.6	224.2	173.2	193.7	368.7	146.6	223.2	172.6	192.8	366.1	225	24.5	2"	180	16.1	2"	270	29.1	3"
EAW-VD15S2ZB370C2-425AXSP12	125	193.1	148.3	166.3	320.2	124.5	191.4	147.5	165.1	316.8	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370C2-432AXSP16	115.2	177.9	136.8	153.4	-	114.7	176.5	135.7	152.1	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370C2-525AXSP16	138.1	209.3	162.2	180.9	-	137.2	207.2	161	179.5	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C2-532AXSP16	129.2	197.7	152.5	170.5	-	128.6	195.6	151.4	169	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C2-625AXSP16	151.7	226.6	176.9	196.4	365.2	150.6	224.3	175.3	194.6	361.2	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C2-632AXSP16	144	217.2	168.8	188.1	353.6	143	215.2	167.5	186.3	349.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C4-425AXSP12	125	193.1	148.3	166.3	320.2	124.5	191.4	147.5	165.1	316.8	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370C4-432AXSP16	115.2	177.9	136.8	153.4	-	114.7	176.5	135.7	152.1	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370C4-525AXSP16	138.1	209.3	162.2	180.9	-	137.2	207.2	161	179.5	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C4-532AXSP16	129.2	197.7	152.5	170.5	-	128.6	195.6	151.4	169	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C4-625AXSP16	151.7	226.6	176.9	196.4	365.2	150.6	224.3	175.3	194.6	361.2	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C4-632AXSP16	144	217.2	168.8	188.1	353.6	143	215.2	167.5	186.3	349.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C5-425AXSP12	125	193.1	148.3	166.3	320.2	124.5	191.4	147.5	165.1	316.8	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370C5-432AXSP16	115.2	177.9	136.8	153.4	-	114.7	176.5	135.7	152.1	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370C5-525AXSP16	138.1	209.3	162.2	180.9	-	137.2	207.2	161	179.5	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C5-532AXSP16	129.2	197.7	152.5	170.5	-	128.6	195.6	151.4	169	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C5-625AXSP16	151.7	226.6	176.9	196.4	365.2	150.6	224.3	175.3	194.6	361.2	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C5-632AXSP16	144	217.2	168.8	188.1	353.6	143	215.2	167.5	186.3	349.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C8-425AXSP12	125	193.1	148.3	166.3	320.2	124.5	191.4	147.5	165.1	316.8	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370C8-432AXSP16	115.2	177.9	136.8	153.4	-	114.7	176.5	135.7	152.1	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370C8-525AXSP16	138.1	209.3	162.2	180.9	-	137.2	207.2	161	179.5	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C8-532AXSP16	129.2	197.7	152.5	170.5	-	128.6	195.6	151.4	169	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370C8-625AXSP16	151.7	226.6	176.9	196.4	365.2	150.6	224.3	175.3	194.6	361.2	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370C8-632AXSP16	144	217.2	168.8	188.1	353.6	143	215.2	167.5	186.3	349.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K2-425AXSP12	120.1	185.6	142.8	160	307.4	119.9	184.3	142	158.9	304.3	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370K2-432AXSP16	111.4	171.9	131.9	147.8	-	110.7	170.3	131.1	146.9	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370K2-525AXSP16	132.7	200.7	155.7	173.6	-	131.9	198.9	154.5	172.2	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K2-532AXSP16	124.5	189.9	146.7	164	-	123.8	188.3	145.6	162.8	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K2-625AXSP16	145.4	217	169.5	188.2	349.1	144.5	214.7	167.9	186.4	344.8	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K2-632AXSP16	138.3	208.5	162	180.5	338.8	137.5	206.3	160.7	179	334.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K4-425AXSP12	120.1	185.6	142.8	160	307.4	119.9	184.3	142	158.9	304.3	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370K4-432AXSP16	111.4	171.9	131.9	147.8	-	110.7	170.3	131.1	146.9	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370K4-525AXSP16	132.7	200.7	155.7	173.6	-	131.9	198.9	154.5	172.2	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K4-532AXSP16	124.5	189.9	146.7	164	-	123.8	188.3	145.6	162.8	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K4-625AXSP16	145.4	217	169.5	188.2	349.1	144.5	214.7	167.9	186.4	344.8	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K4-632AXSP16	138.3	208.5	162	180.5	338.8	137.5	206.3	160.7	179	334.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K5-425AXSP12	120.1	185.6	142.8	160	307.4	119.9	184.3	142	158.9	304.3	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370K5-432AXSP16	111.4	171.9	131.9	147.8	-	110.7	170.3	131.1	146.9	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370K5-525AXSP16	132.7	200.7	155.7	173.6	-	131.9	198.9	154.5	172.2	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K5-532AXSP16	124.5	189.9	146.7	164	-	123.8	188.3	145.6	162.8	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K5-625AXSP16	145.4	217	169.5	188.2	349.1	144.5	214.7	167.9	186.4	344.8	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K5-632AXSP16	138.3	208.5	162	180.5	338.8	137.5	206.3	160.7	179	334.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K8-425AXSP12	120.1	185.6	142.8	160	307.4	119.9	184.3	142	158.9	304.3	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB370K8-432AXSP16	111.4	171.9	131.9	147.8	-	110.7	170.3	131.1	146.9	-	146	26.3	2"	117	19.9	1-1/2"	176	36.9	2"
EAW-VD15S2ZB370K8-525AXSP16	132.7	200.7	155.7	173.6	-	131.9	198.9	154.5	172.2	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K8-532AXSP16	124.5	189.9	146.7	164	-	123.8	188.3	145.6	162.8	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB370K8-625AXSP16	145.4	217	169.5	188.2	349.1	144.5	214.7	167.9	186.4	344.8	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB370K8-632AXSP16	138.3	208.5	162	180.5	338.8	137.5	206.3	160.7	179	334.5	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB400B3-425AXSP12	121.7	188.2	144.7	162.2	311														

EAW-VD15S2ZB50B3-525AXSP12	147	225.4	174.1	194.6	370.6	146.7	223.7	173	193.4	366.9	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50B3-532AXSP16	138.6	212.3	163.7	183.2	-	137.9	210.4	162.5	181.8	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB50B3-625AXSP16	162.3	243.2	189.6	210.9	-	161.5	241.2	188.2	209.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50B3-625AXSP16	154.3	233.5	181.2	202	-	153.7	231.4	180	200.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C2-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C2-432AXSP12	128.9	201.6	154.1	173	337.8	128.7	200.1	153.3	172.1	334.7	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C2-525AXSP12	154.8	237.4	183.1	204.7	390.8	154.2	235.5	182.1	203.3	387.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C2-532AXSP12	144.3	223.3	171.4	192.2	370.6	143.8	221.5	170.5	191.2	367	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C2-625AXSP16	171.5	257.7	200.6	223.3	-	170.6	255.2	198.9	221.3	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C2-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C3-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C3-432AXSP12	128.9	201.6	154.1	173	337.8	128.7	200.1	153.3	172.1	334.7	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C3-525AXSP12	154.8	237.4	183.1	204.7	390.8	154.2	235.5	182.1	203.3	387.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C3-532AXSP12	144.3	223.3	171.4	192.2	370.6	143.8	221.5	170.5	191.2	367	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C3-625AXSP16	171.5	257.7	200.6	223.3	-	170.6	255.2	198.9	221.3	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C3-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C4-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C4-432AXSP12	128.9	201.6	154.1	173	337.8	128.7	200.1	153.3	172.1	334.7	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C4-525AXSP12	154.8	237.4	183.1	204.7	390.8	154.2	235.5	182.1	203.3	387.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C4-532AXSP12	144.3	223.3	171.4	192.2	370.6	143.8	221.5	170.5	191.2	367	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C4-625AXSP16	171.5	257.7	200.6	223.3	-	170.6	255.2	198.9	221.3	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C4-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C5-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C5-432AXSP12	128.9	201.6	154.1	173	337.8	128.7	200.1	153.3	172.1	334.7	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C5-525AXSP12	154.8	237.4	183.1	204.7	390.8	154.2	235.5	182.1	203.3	387.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C5-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C5-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C8-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C8-432AXSP12	128.9	201.6	154.1	173	337.8	128.7	200.1	153.3	172.1	334.7	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C8-525AXSP12	154.8	237.4	183.1	204.7	390.8	154.2	235.5	182.1	203.3	387.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C8-625AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C8-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C9-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C9-425AXSP12	140.2	217.2	166.4	186.9	-	139.8	215.5	165.7	185.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C9-425AXSP12	128.9	201.6	154.1	173	337.8	128.7	200.1	153.3	172.1	334.7	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50C9-525AXSP12	154.8	237.4	183.1	204.7	390.8	154.2	235.5	182.1	203.3	387.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50C9-625AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50C9-632AXSP16	162.2	245.9	190.6	212.5	-	161.2	243.5	189.2	211	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K2-425AXSP12	134.3	208	159.6	178.9	-	134	206.5	158.7	178.1	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K2-432AXSP12	124.1	193.7	148	166.4	324	123.8	192.3	147.5	165.5	321.2	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K2-525AXSP12	147.7	226.2	174.6	195.2	372	147.2	224.7	173.8	193.9	368.5	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50K3-432AXSP16	138.8	212.7	163.9	183.5	-	138.2	211.1	163	182.1	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB50K2-625AXSP16	163.3	244.7	190.7	211.9	-	162.3	242.4	189.1	210.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K2-632AXSP16	155	234.3	181.8	202.7	-	154.1	232.4	180.5	201	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K3-425AXSP12	134.3	208	159.6	178.9	-	134	206.5	158.7	178.1	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K3-432AXSP12	124.1	193.7	148	166.4	324	123.8	192.3	147.5	165.5	321.2	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K3-525AXSP12	147.7	226.2	174.6	195.2	372	147.2	224.7	173.8	193.9	368.5	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50K3-532AXSP16	138.8	212.7	163.9	183.5	-	138.2	211.1	163	182.1	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB50K3-625AXSP16	163.3	244.7	190.7	211.9	-	162.3	242.4	189.1	210.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K3-632AXSP16	155	234.3	181.8	202.7	-	154.1	232.4	180.5	201	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K4-425AXSP12	134.3	208	159.6	178.9	-	134	206.5	158.7	178.1	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K4-432AXSP12	124.1	193.7	148	166.4	324	123.8	192.3	147.5	165.5	321.2	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K4-432AXSP12	147.7	226.2	174.6	195.2	372	147.2	224.7	173.8	193.9	368.5	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50K4-525AXSP16	138.8	212.7	163.9	183.5	-	138.2	211.1	163	182.1	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB50K4-625AXSP16	163.3	244.7	190.7	211.9	-	162.3	242.4	189.1	210.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K4-632AXSP16	155	234.3	181.8	202.7	-	154.1	232.4	180.5	201	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K5-425AXSP12	134.3	208	159.6	178.9	-	134	206.5	158.7	178.1	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K5-432AXSP12	124.1	193.7	148	166.4	324	123.8	192.3	147.5	165.5	321.2	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K5-525AXSP12	147.7	226.2	174.6	195.2	372	147.2	224.7	173.8	193.9	368.5	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB50K5-532AXSP16	138.8	212.7	163.9	183.5	-	138.2	211.1	163	182.1	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD15S2ZB50K5-625AXSP16	163.3	244.7	190.7	211.9	-	162.3	242.4	189.1	210.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K5-632AXSP16	155	234.3	181.8	202.7	-	154.1	232.4	180.5	201	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB50K8-425AXSP12	134.3	208	159.6	178.9	-	134	206.5	158.7	178.1	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K8-432AXSP12	124.1	193.7	148	166.4	324	123.8	192.3	147.5	165.5	321.2	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB50K8-525AXSP12	147.7	226.2	174.6	195.2	372	147.2	224.7	173.8	193.9	368.5	248	19.3	3"	1					

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S2ZB750C5-432AXSP12	138.2	216.3	165	185.6	-	138.2	215	164.4	184.8	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750C5-525AXSP12	165.8	254.7	195.9	219.3	-	165.5	253	195.3	218.2	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750C5-532AXSP12	154.5	239.6	183.6	206.2	398.5	154.2	238	183	205.1	395.2	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750C5-625AXSP16	183.3	275.9	214.5	238.8	-	182.4	273.7	213.3	237.5	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750C5-632AXSP12	170.7	261.9	202.1	226	431.1	170.5	260.5	201.3	225	427.5	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750C8-425AXSP12	150	233	178.6	200.4	-	149.9	231.9	177.8	199.5	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750C8-432AXSP12	138.2	216.3	165	185.6	-	138.2	215	164.4	184.8	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750C8-525AXSP12	165.8	254.7	195.9	219.3	-	165.5	253	195.3	218.2	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750C8-532AXSP12	154.5	239.6	183.6	206.2	398.5	154.2	238	183	205.1	395.2	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750C8-625AXSP16	183.3	275.9	214.5	238.8	-	182.4	273.7	213.3	237.5	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750C8-632AXSP12	170.7	261.9	202.1	226	431.1	170.5	260.5	201.3	225	427.5	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750C9-425AXSP12	150	233	178.6	200.4	-	149.9	231.9	177.8	199.5	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750C9-432AXSP12	138.2	216.3	165	185.6	-	138.2	215	164.4	184.8	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750C9-525AXSP12	165.8	254.7	195.9	219.3	-	165.5	253	195.3	218.2	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750C9-532AXSP12	154.5	239.6	183.6	206.2	398.5	154.2	238	183	205.1	395.2	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750C9-625AXSP16	183.3	275.9	214.5	238.8	-	182.4	273.7	213.3	237.5	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750C9-632AXSP12	170.7	261.9	202.1	226	431.1	170.5	260.5	201.3	225	427.5	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750K2-425AXSP12	145.1	225.2	172.6	193.9	-	144.9	223.8	172.1	193	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K2-432AXSP12	134	209.7	160	180.1	-	133.8	208.5	159.4	179	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K2-525AXSP12	159.9	245.6	189.2	211.7	404.8	159.5	244	188.2	210.5	401.4	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K2-532AXSP12	149.3	231.5	177.7	199.1	384.7	149.1	230	176.8	198.1	381	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K2-625AXSP12	173.7	263.9	204.7	228.2	430	173.5	262.2	203.6	227	425.8	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750K2-632AXSP16	167.6	254.4	196.9	219.7	-	166.8	252.2	195.8	218.1	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750K3-425AXSP12	145.1	225.2	172.6	193.9	-	144.9	223.8	172.1	193	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K3-432AXSP12	134	209.7	160	180.1	-	133.8	208.5	159.4	179	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K3-525AXSP12	159.9	245.6	189.2	211.7	404.8	159.5	244	188.2	210.5	401.4	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K3-532AXSP12	149.3	231.5	177.7	199.1	384.7	149.1	230	176.8	198.1	381	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K3-625AXSP12	173.7	263.9	204.7	228.2	430	173.5	262.2	203.6	227	425.8	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750K3-632AXSP16	167.6	254.4	196.9	219.7	-	166.8	252.2	195.8	218.1	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750K4-425AXSP12	145.1	225.2	172.6	193.9	-	144.9	223.8	172.1	193	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K4-432AXSP12	134	209.7	160	180.1	-	133.8	208.5	159.4	179	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K4-525AXSP12	159.9	245.6	189.2	211.7	404.8	159.5	244	188.2	210.5	401.4	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K4-532AXSP12	149.3	231.5	177.7	199.1	384.7	149.1	230	176.8	198.1	381	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K4-625AXSP12	173.7	263.9	204.7	228.2	430	173.5	262.2	203.6	227	425.8	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750K4-632AXSP16	167.6	254.4	196.9	219.7	-	166.8	252.2	195.8	218.1	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750K5-425AXSP12	145.1	225.2	172.6	193.9	-	144.9	223.8	172.1	193	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K5-432AXSP12	134	209.7	160	180.1	-	133.8	208.5	159.4	179	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K5-525AXSP12	159.9	245.6	189.2	211.7	404.8	159.5	244	188.2	210.5	401.4	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K5-532AXSP12	149.3	231.5	177.7	199.1	384.7	149.1	230	176.8	198.1	381	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K5-632AXSP16	167.6	254.4	196.9	219.7	-	166.8	252.2	195.8	218.1	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750K6-425AXSP12	145.1	225.2	172.6	193.9	-	144.9	223.8	172.1	193	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K6-432AXSP12	134	209.7	160	180.1	-	133.8	208.5	159.4	179	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K6-525AXSP12	159.9	245.6	189.2	211.7	404.8	159.5	244	188.2	210.5	401.4	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K6-532AXSP12	149.3	231.5	177.7	199.1	384.7	149.1	230	176.8	198.1	381	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K6-625AXSP12	173.7	263.9	204.7	228.2	430	173.5	262.2	203.6	227	425.8	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD15S2ZB750K6-632AXSP16	167.6	254.4	196.9	219.7	-	166.8	252.2	195.8	218.1	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750K9-425AXSP12	145.1	225.2	172.6	193.9	-	144.9	223.8	172.1	193	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K9-432AXSP12	134	209.7	160	180.1	-	133.8	208.5	159.4	179	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750K9-525AXSP12	159.9	245.6	189.2	211.7	404.8	159.5	244	188.2	210.5	401.4	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K9-532AXSP12	149.3	231.5	177.7	199.1	384.7	149.1	230	176.8	198.1	381	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750K9-632AXSP16	167.6	254.4	196.9	219.7	-	166.8	252.2	195.8	218.1	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750R3-425AXSP12	142.2	220.5	169.1	189.7	-	142.1	219.1	168.4	188.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750R3-432AXSP12	131.4	205.3	156.7	176.4	-	131.1	204.1	156.1	175.4	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD15S2ZB750R3-525AXSP12	156.3	239.8	184.9	207.1	395.5	156.1	238.2	184.2	205.9	391.7	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750R3-532AXSP12	146.1	226.3	173.9	195.1	375.8	145.9	225.2	173	194	372.7	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD15S2ZB750R3-625AXSP16	172.5	259.2	201.5	224.3	-	171.8	256.9	200.5	222.8	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZB750R3-632AXSP16	163.8	248.4	192.4	214.9	-	163.2	246.6	191.3	213.3	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD15S2ZK017G7-425AXSP08	180.3	285.5	217.2	244.9	481.6	180.8	283.9	216.5	244	477.9	304	14.9	3"	244	9.9	3"	365	21	3"
EAW-VD15S2ZK017G7-432AXSP08	164.4	262.7	199	225	445.5	164.9	261.6	198.7	224.3	442.4	304	14.9	3"	244	9.9	3"	365	21	3"
EAW-VD15S2ZK017G7-525AXSP12	210.2	323.5	248.7	278.7	-	209.5	320.9	247.5	276.9	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK017G7-532AXSP12	194.1	301.3	230.7	259	-	193.7	299	229.8	257.4	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK017G7-625AXSP12	232.3	352.8	273.2	305	-	231.2	349.8	271.3	302.8	-	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK017G7-632AXSP12	217.1	333.3	256.6	287.3	-	216.6	330.6	255.3	285.3	-	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK370C2-425AXSP12	131.5	201.9	155.5	174.2	333.6	130.8	200.2	154.5	172.7	329.8	203	23.8	2"	162	15.7	2"	244		

EAW-VD15S2ZK370K5-425AXSP12	126.8	194.6	149.9	167.8	320.8	126.2	192.8	148.9	166.4	317.3	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK370K5-432AXSP12	117.5	181.8	139.7	156.7	302.2	116.8	180.1	138.7	155.4	298.9	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK370K5-525AXSP12	138.9	210.9	163.5	182.4	343.8	138.1	208.8	162.3	180.8	339.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK370K5-532AXSP16	130.8	199	154	171.8	-	130.1	196.8	152.6	170.4	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK370K5-625AXSP16	152.8	226.8	177.5	196.9	363.8	151.5	224.3	175.9	194.9	359.1	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK370K5-632AXSP16	145.4	218	169.9	188.8	352.9	144.2	215.5	168.4	187.1	348.5	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK370K8-425AXSP12	126.8	194.6	149.9	167.8	320.8	126.2	192.8	148.9	166.4	317.3	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK370K8-432AXSP12	117.5	181.8	139.7	156.7	302.2	116.8	180.1	138.7	155.4	298.9	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK370K8-525AXSP12	138.9	210.9	163.5	182.4	343.8	138.1	208.8	162.3	180.8	339.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK370K8-532AXSP16	130.8	199	154	171.8	-	130.1	196.8	152.6	170.4	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK370K8-625AXSP16	152.8	226.8	177.5	196.9	363.8	151.5	224.3	175.9	194.9	359.1	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK370K8-632AXSP16	145.4	218	169.9	188.8	352.9	144.2	215.5	168.4	187.1	348.5	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400B3-425AXSP12	128.6	197.3	152.1	170.3	325.8	128	195.5	150.9	168.9	321.8	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400B3-432AXSP12	119.1	184.4	141.4	158.8	306.1	118.4	182.7	140.6	157.6	302.8	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400B3-525AXSP12	140.9	214	165.8	185	348.9	140	211.9	164.7	183.5	344.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK400B3-532AXSP16	132.7	201.7	156	174.3	-	131.8	199.8	154.8	172.6	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK400B3-625AXSP16	154.9	230.1	180.2	199.7	369.1	153.7	227.5	178.4	197.7	364.3	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400B3-632AXSP16	147.5	221.2	172.3	191.6	358.2	146.3	218.7	170.8	189.9	353.8	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400C3-425AXSP12	131.5	201.9	155.5	174.2	333.6	130.8	200.2	154.5	172.7	329.8	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400C3-432AXSP12	121.7	188.2	144.5	162.1	313.3	121	186.8	143.6	160.8	309.8	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400C3-525AXSP12	144.6	219.9	170.3	190.1	359.1	143.9	217.7	169	188.3	354.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK400C3-532AXSP16	135.7	206.8	159.9	178.4	-	134.8	204.4	158.5	176.8	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK400C3-625AXSP16	159.4	236.9	185.4	205.8	-	158.1	234.2	183.5	203.7	375.6	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400C3-632AXSP16	151.4	227.2	176.9	197	368.6	150.1	224.8	175.3	194.9	363.4	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400C9-425AXSP12	131.5	201.9	155.5	174.2	333.6	130.8	200.2	154.5	172.7	329.8	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400C9-432AXSP12	121.7	188.2	144.5	162.1	313.3	121	186.8	143.6	160.8	309.8	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400C9-525AXSP12	144.6	219.9	170.3	190.1	359.1	143.9	217.7	169	188.3	354.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK400C9-532AXSP16	135.7	206.8	159.9	178.4	-	134.8	204.4	158.5	176.8	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK400C9-625AXSP16	159.4	236.9	185.4	205.8	-	158.1	234.2	183.5	203.7	375.6	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400C9-632AXSP16	151.4	227.2	176.9	197	368.6	150.1	224.8	175.3	194.9	363.4	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400K3-425AXSP12	126.8	194.6	149.9	167.8	320.8	126.2	192.8	148.9	166.4	317.3	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400K3-432AXSP12	117.5	181.8	139.7	156.7	302.2	116.8	180.1	138.7	155.4	298.9	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400K3-525AXSP12	138.9	210.9	163.5	182.4	343.8	138.1	208.8	162.3	180.8	339.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK400K3-532AXSP16	130.8	199	154	171.8	-	130.1	196.8	152.6	170.4	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK400K3-625AXSP16	152.8	226.8	177.5	196.9	363.8	151.5	224.3	175.9	194.9	359.1	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400K3-632AXSP16	145.4	218	169.9	188.8	352.9	144.2	215.5	168.4	187.1	348.5	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400K9-425AXSP12	126.8	194.6	149.9	167.8	320.8	126.2	192.8	148.9	166.4	317.3	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400K9-432AXSP12	117.5	181.8	139.7	156.7	302.2	116.8	180.1	138.7	155.4	298.9	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400K9-525AXSP12	138.9	210.9	163.5	182.4	343.8	138.1	208.8	162.3	180.8	339.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK400K9-532AXSP16	130.8	199	154	171.8	-	130.1	196.8	152.6	170.4	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK400K9-625AXSP16	152.8	226.8	177.5	196.9	363.8	151.5	224.3	175.9	194.9	359.1	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400K9-632AXSP16	145.4	218	169.9	188.8	352.9	144.2	215.5	168.4	187.1	348.5	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400R3-425AXSP12	129.5	198.7	153.1	171.5	328.2	128.9	197.2	152.2	170.1	324.7	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400R3-432AXSP12	120.1	185.9	142.5	160.1	308.8	119.4	184.3	141.8	158.7	305.6	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK400R3-525AXSP12	141.8	215.5	167.2	186.3	351.7	141.2	213.4	165.8	184.7	347.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK400R3-532AXSP16	133.6	203.4	157.3	175.5	-	132.7	201.2	155.9	174.1	-	180	29.7	2"	144	19.6	2"	216	41.6	2"
EAW-VD15S2ZK400R3-625AXSP16	156.1	231.8	181.3	201.2	372	154.9	229.3	179.8	199.2	367.2	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK400R3-632AXSP16	148.5	223	173.5	193.1	361.1	147.3	220.5	172	191.2	356.3	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK500B3-425AXSP12	141.6	218.1	167.8	187.8	-	141	216.2	166.6	186.5	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK500B3-432AXSP12	131	203.1	155.7	174.8	338.3	130.4	201.4	154.7	173.7	335	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK500B3-525AXSP12	155.7	237	183.4	204.9	388.2	155.2	235	182.3	203.3	383.8	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK500B3-532AXSP12	145.9	224.1	172.7	193.1	369.7	145.2	222.2	171.5	191.7	365.9	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK500B3-625AXSP12	168.9	254.5	198.1	220.5	411.2	168.2	251.9	196.6	218.6	406.7	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK500B3-632AXSP16	162.9	245.3	190.6	212.4	-	161.7	242.7	189.1	210.4	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK550C2-425AXSP12	147.7	228	175.2	196.2	-	147.1	226	173.9	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550C2-432AXSP12	136.2	211.6	162	182	-	135.8	209.8	160.9	180.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550C2-525AXSP12	163.4	249.1	192.5	215.1	408.4	162.7	246.7	191.2	213.4	403.9	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550C2-532AXSP12	152.3	234.5	180.4	202.1	387.2	151.6	232.3	179.3	200.6	383	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550C2-625AXSP12	178.2	268.5	209	232.5	435.2	177.4	266	207.3	230.6	430.2	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550C2-632AXSP12	168.5	256.4	198.7	221.5	419	167.5	253.9	197	219.9	414.3	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550C3-425AXSP12	147.7	228	175.2	196.2	-	147.1	226	173.9	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550C3-432AXSP12	136.2	211.6	162	182	-	135.8	209.8	160.9	180.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550C3-525AXSP12	163.4	249.1	192.5	215.1	408.4	162.7	246.7	191.2	213.4	4									

EAW-VD15S2ZK550K3-632AXSP16	163.4	246.1	191.3	212.8	-	162.3	243.5	189.5	211.1	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK550K4-425AXSP12	142.1	218.5	168.1	188.2	-	141.3	216.7	167	186.9	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K4-432AXSP12	131.3	203.6	156	175.2	-	130.9	202.3	155.3	174.1	336.4	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K4-525AXSP12	156.2	237.8	184	205.3	389.5	155.5	235.7	182.7	203.7	385	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K4-532AXSP12	146.1	224.6	173	193.8	370.5	145.5	222.6	172.1	192.4	366.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K4-625AXSP12	169.7	255.4	198.7	221.3	412.7	168.8	253	197.4	219.3	408	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550K4-632AXSP16	163.4	246.1	191.3	212.8	-	162.3	243.5	189.5	211.1	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK550K5-425AXSP12	142.1	218.5	168.1	188.2	-	141.3	216.7	167	186.9	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K5-432AXSP12	131.3	203.6	156	175.2	-	130.9	202.3	155.3	174.1	336.4	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K5-525AXSP12	156.2	237.8	184	205.3	389.5	155.5	235.7	182.7	203.7	385	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K5-532AXSP12	146.1	224.6	173	193.8	370.5	145.5	222.6	172.1	192.4	366.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K5-625AXSP12	169.7	255.4	198.7	221.3	412.7	168.8	253	197.4	219.3	408	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550K5-632AXSP16	163.4	246.1	191.3	212.8	-	162.3	243.5	189.5	211.1	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK550K8-425AXSP12	142.1	218.5	168.1	188.2	-	141.3	216.7	167	186.9	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K8-432AXSP12	131.3	203.6	156	175.2	-	130.9	202.3	155.3	174.1	336.4	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K8-525AXSP12	156.2	237.8	184	205.3	389.5	155.5	235.7	182.7	203.7	385	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K8-532AXSP12	146.1	224.6	173	193.8	370.5	145.5	222.6	172.1	192.4	366.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K8-625AXSP12	169.7	255.4	198.7	221.3	412.7	168.8	253	197.4	219.3	408	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550K8-632AXSP16	163.4	246.1	191.3	212.8	-	162.3	243.5	189.5	211.1	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK550K9-425AXSP12	142.1	218.5	168.1	188.2	-	141.3	216.7	167	186.9	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K9-432AXSP12	131.3	203.6	156	175.2	-	130.9	202.3	155.3	174.1	336.4	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550K9-525AXSP12	156.2	237.8	184	205.3	389.5	155.5	235.7	182.7	203.7	385	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K9-532AXSP12	146.1	224.6	173	193.8	370.5	145.5	222.6	172.1	192.4	366.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550K9-625AXSP12	169.7	255.4	198.7	221.3	412.7	168.8	253	197.4	219.3	408	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550K9-632AXSP16	163.4	246.1	191.3	212.8	-	162.3	243.5	189.5	211.1	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD15S2ZK550R3-425AXSP12	146.1	224.9	172.9	193.9	-	145.3	223.1	171.8	192.3	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550R3-432AXSP12	135.1	209.4	160.6	180.1	-	134.6	207.8	159.7	179.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK550R3-525AXSP12	160.6	244.8	189.3	211.4	401.1	159.9	242.7	188.2	209.9	396.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550R3-532AXSP12	150.2	231.1	177.9	199.3	381.6	149.6	229.2	177	197.9	377.8	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK550R3-625AXSP12	174.5	263.1	204.6	227.9	425.8	173.8	260.5	203.3	225.9	420.7	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK550R3-632AXSP12	165.4	252	195	217.7	411.6	164.8	249.7	193.8	216	406.9	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C2-425AXSP12	158.9	245.4	188.6	211.4	-	158.5	243.8	187.5	210.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C2-432AXSP12	146.5	227.7	174.3	195.8	-	146	226.1	173.4	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C2-525AXSP12	175.4	268.3	207.2	231.7	-	175	266.1	205.8	230.1	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C2-532AXSP12	163.7	252.6	194.1	217.4	-	163.2	250.5	192.9	215.9	414	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C2-625AXSP12	191.6	289.2	224.7	250.5	469.9	190.7	286.9	223.2	248.5	465.1	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C2-632AXSP12	181.2	276.1	213.8	238.5	452.4	180.4	274.1	212.3	236.8	448	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C3-425AXSP12	158.9	245.4	188.6	211.4	-	158.5	243.8	187.5	210.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C3-432AXSP12	146.5	227.7	174.3	195.8	-	146	226.1	173.4	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C3-525AXSP12	175.4	268.3	207.2	231.7	-	175	266.1	205.8	230.1	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C3-532AXSP12	163.7	252.6	194.1	217.4	-	163.2	250.5	192.9	215.9	414	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C3-625AXSP12	191.6	289.2	224.7	250.5	469.9	190.7	286.9	223.2	248.5	465.1	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C3-632AXSP12	181.2	276.1	213.8	238.5	452.4	180.4	274.1	212.3	236.8	448	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C4-425AXSP12	158.9	245.4	188.6	211.4	-	158.5	243.8	187.5	210.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C4-432AXSP12	146.5	227.7	174.3	195.8	-	146	226.1	173.4	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C4-525AXSP12	175.4	268.3	207.2	231.7	-	175	266.1	205.8	230.1	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C4-532AXSP12	163.7	252.6	194.1	217.4	-	163.2	250.5	192.9	215.9	414	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C4-625AXSP12	191.6	289.2	224.7	250.5	469.9	190.7	286.9	223.2	248.5	465.1	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C4-632AXSP12	181.2	276.1	213.8	238.5	452.4	180.4	274.1	212.3	236.8	448	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C5-425AXSP12	158.9	245.4	188.6	211.4	-	158.5	243.8	187.5	210.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C5-432AXSP12	146.5	227.7	174.3	195.8	-	146	226.1	173.4	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C5-525AXSP12	175.4	268.3	207.2	231.7	-	175	266.1	205.8	230.1	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C5-532AXSP12	163.7	252.6	194.1	217.4	-	163.2	250.5	192.9	215.9	414	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C5-625AXSP12	191.6	289.2	224.7	250.5	469.9	190.7	286.9	223.2	248.5	465.1	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C5-632AXSP12	181.2	276.1	213.8	238.5	452.4	180.4	274.1	212.3	236.8	448	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C8-425AXSP12	158.9	245.4	188.6	211.4	-	158.5	243.8	187.5	210.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C8-432AXSP12	146.5	227.7	174.3	195.8	-	146	226.1	173.4	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C8-525AXSP12	175.4	268.3	207.2	231.7	-	175	266.1	205.8	230.1	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C8-532AXSP12	163.7	252.6	194.1	217.4	-	163.2	250.5	192.9	215.9	414	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD15S2ZK750C8-625AXSP12	191.6	289.2	224.7	250.5	469.9	190.7	286.9	223.2	248.5	465.1	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C8-632AXSP12	181.2	276.1	213.8	238.5	452.4	180.4	274.1	212.3	236.8	448	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD15S2ZK750C9-425AXSP12	158.9	245.4	188.6	211.4	-	158.5	243.8	187.5	210.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C9-432AXSP12	146.5	227.7	174.3	195.8	-	146	226.1	173.4	194.7	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD15S2ZK750C9-525AXSP12	175.4	268.3	207.2	231.7	-	175	266.1	205.8	230.1	-	248	21	3"	198					

EAW-VD1552ZK750K9-625AXSP12	184.7	278.5	216.4	241.1	451.7	183.9	275.9	215.1	239.4	447	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD1552ZK750K9-632AXSP12	174.8	266.3	206.2	230.2	436.1	174	264.1	204.7	228.6	431.4	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD1552ZK750R3-425AXSP12	150.7	232.5	178.5	200.3	-	150.1	230.8	177.5	198.8	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD1552ZK750R3-432AXSP12	139.4	216.5	165.8	186.1	-	139	215	165	185.1	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD1552ZK750R3-525AXSP12	165.9	252.7	195.5	218.2	-	165.2	250.7	194.2	216.7	410.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD1552ZK750R3-532AXSP12	155.2	238.8	183.9	205.8	394.6	154.7	236.9	182.8	204.5	390.9	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD1552ZK750R3-625AXSP12	180.3	271.7	211.5	235.3	440.5	179.5	269.5	210	233.6	435.4	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD1552ZK750R3-632AXSP12	170.8	260.1	201.5	224.9	425.7	170.3	258	200.3	223.3	421.1	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD1553PB370C2-425AXSP08	162.3	251.7	192.8	216.7	-	162.1	250.6	192.2	215.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C2-432AXSP08	150.2	234.7	179.3	201.5	-	150.1	233.6	178.4	200.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C2-525AXSP08	180.1	275.9	212.7	238.2	455	179.9	274.5	212.2	237	451.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C2-532AXSP08	168.8	261.5	200.8	225.3	434.2	168.7	260.1	200.1	224.5	431.3	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C2-625AXSP08	192	291.8	226.3	252.3	475.5	192.1	290.1	225.5	251.4	471.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C2-632AXSP08	183.1	281.1	216.7	242.6	461.6	182.8	279.5	215.9	241.3	457.9	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C4-425AXSP08	162.3	251.7	192.8	216.7	-	162.1	250.6	192.2	215.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C4-432AXSP08	150.2	234.7	179.3	201.5	-	150.1	233.6	178.4	200.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C4-525AXSP08	180.1	275.9	212.7	238.2	455	179.9	274.5	212.2	237	451.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C4-532AXSP08	168.8	261.5	200.8	225.3	434.2	168.7	260.1	200.1	224.5	431.3	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C4-625AXSP08	192	291.8	226.3	252.3	475.5	192.1	290.1	225.5	251.4	471.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C4-632AXSP08	183.1	281.1	216.7	242.6	461.6	182.8	279.5	215.9	241.3	457.9	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C5-425AXSP08	162.3	251.7	192.8	216.7	-	162.1	250.6	192.2	215.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C5-432AXSP08	150.2	234.7	179.3	201.5	-	150.1	233.6	178.4	200.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C5-525AXSP08	180.1	275.9	212.7	238.2	455	179.9	274.5	212.2	237	451.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C5-532AXSP08	168.8	261.5	200.8	225.3	434.2	168.7	260.1	200.1	224.5	431.3	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C5-625AXSP08	192	291.8	226.3	252.3	475.5	192.1	290.1	225.5	251.4	471.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C5-632AXSP08	183.1	281.1	216.7	242.6	461.6	182.8	279.5	215.9	241.3	457.9	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C8-425AXSP08	162.3	251.7	192.8	216.7	-	162.1	250.6	192.2	215.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C8-432AXSP08	150.2	234.7	179.3	201.5	-	150.1	233.6	178.4	200.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370C8-525AXSP08	180.1	275.9	212.7	238.2	455	179.9	274.5	212.2	237	451.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C8-532AXSP08	168.8	261.5	200.8	225.3	434.2	168.7	260.1	200.1	224.5	431.3	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370C8-625AXSP08	192	291.8	226.3	252.3	475.5	192.1	290.1	225.5	251.4	471.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370C8-632AXSP08	183.1	281.1	216.7	242.6	461.6	182.8	279.5	215.9	241.3	457.9	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K2-425AXSP08	156.2	242.3	185.8	208.4	-	156.2	241	185.2	207.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K2-432AXSP08	144.9	226.4	172.8	194.2	-	144.7	224.9	172.4	193.6	376.4	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K2-525AXSP08	173.1	265.2	204.7	228.8	436.3	172.9	263.7	203.9	227.9	432.8	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K2-532AXSP08	162.7	251.6	193.6	216.7	417.4	162.6	250.3	192.8	215.8	414.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K2-625AXSP08	184.9	280.6	217.5	242.8	456.4	184.5	278.7	216.6	241.4	452.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K2-632AXSP08	176	269.9	208.4	233.2	442.9	175.7	268.3	207.5	232.1	439.7	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K4-425AXSP08	156.2	242.3	185.8	208.4	-	156.2	241	185.2	207.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K4-432AXSP08	144.9	226.4	172.8	194.2	-	144.7	224.9	172.4	193.6	376.4	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K4-525AXSP08	173.1	265.2	204.7	228.8	436.3	172.9	263.7	203.9	227.9	432.8	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K4-532AXSP08	162.7	251.6	193.6	216.7	417.4	162.6	250.3	192.8	215.8	414.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K4-625AXSP08	184.9	280.6	217.5	242.8	456.4	184.5	278.7	216.6	241.4	452.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K4-632AXSP08	176	269.9	208.4	233.2	442.9	175.7	268.3	207.5	232.1	439.7	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K5-425AXSP08	156.2	242.3	185.8	208.4	-	156.2	241	185.2	207.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K5-432AXSP08	144.9	226.4	172.8	194.2	-	144.7	224.9	172.4	193.6	376.4	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K5-525AXSP08	173.1	265.2	204.7	228.8	436.3	172.9	263.7	203.9	227.9	432.8	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K5-532AXSP08	162.7	251.6	193.6	216.7	417.4	162.6	250.3	192.8	215.8	414.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K5-625AXSP08	184.9	280.6	217.5	242.8	456.4	184.5	278.7	216.6	241.4	452.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K5-632AXSP08	176	269.9	208.4	233.2	442.9	175.7	268.3	207.5	232.1	439.7	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K8-425AXSP08	156.2	242.3	185.8	208.4	-	156.2	241	185.2	207.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K8-432AXSP08	144.9	226.4	172.8	194.2	-	144.7	224.9	172.4	193.6	376.4	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB370K8-525AXSP08	173.1	265.2	204.7	228.8	436.3	172.9	263.7	203.9	227.9	432.8	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K8-532AXSP08	162.7	251.6	193.6	216.7	417.4	162.6	250.3	192.8	215.8	414.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB370K8-625AXSP08	184.9	280.6	217.5	242.8	456.4	184.5	278.7	216.6	241.4	452.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB370K8-632AXSP08	176	269.9	208.4	233.2	442.9	175.7	268.3	207.5	232.1	439.7	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB400K3-425AXSP08	157.8	244.7	187.3	210.4	-	157.6	243.6	187.1	209.8	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB400K3-432AXSP08	146.3	228.7	174.6	196.5	-	146.3	227.4	174.2	195.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB400K3-525AXSP08	174.1	267.1	205.8	230.5	439.5	174	265.6	205.2	229.4	436.4	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB400K3-532AXSP08	164	254.1	195	218.7	421.5	164	252.8	194.7	218	418.1	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD1553PB400K3-625AXSP08	185.1	281	218.1	243.1	457.1	185.2	279.7	217.6	242.2	453.9	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB400K3-632AXSP08	177	271.8	209.5	234.4	446	177.1	270.2	209.1	233.6	442.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD1553PB400C3-425AXSP08	162.3	251.7	192.8	216.7	-	162.1	250.6	192.2	215.6	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD1553PB400C3-432AXSP08	150.2																		

EAW-VD15S3PB550C2-532AXSP08	188.6	292.8	224.3	251.7	-	188.7	291.6	223.8	251	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C2-625AXSP08	216.4	329.6	254.8	284.8	539.8	216.4	328.3	254.5	283.6	535.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C2-632AXSP08	205.2	315.7	242.9	272.3	520.8	205.3	314.4	242.7	271.1	517.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C3-425AXSP08	180.6	281.5	215.3	242	-	180.6	280.5	214.9	241.5	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C3-432AXSP08	166.6	261.5	199.1	224.2	-	166.6	260.1	198.8	223.8	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C3-525AXSP08	201.6	310.5	238.8	267.5	-	201.7	309.2	238.2	266.7	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C3-532AXSP08	188.6	292.8	224.3	251.7	-	188.7	291.6	223.8	251	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C3-625AXSP08	216.4	329.6	254.8	284.8	539.8	216.4	328.3	254.5	283.6	535.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C3-632AXSP08	205.2	315.7	242.9	272.3	520.8	205.3	314.4	242.7	271.1	517.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C4-425AXSP08	180.6	281.5	215.3	242	-	180.6	280.5	214.9	241.5	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C4-432AXSP08	166.6	261.5	199.1	224.2	-	166.6	260.1	198.8	223.8	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C4-525AXSP08	201.6	310.5	238.8	267.5	-	201.7	309.2	238.2	266.7	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C4-532AXSP08	188.6	292.8	224.3	251.7	-	188.7	291.6	223.8	251	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C4-625AXSP08	216.4	329.6	254.8	284.8	539.8	216.4	328.3	254.5	283.6	535.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C4-632AXSP08	205.2	315.7	242.9	272.3	520.8	205.3	314.4	242.7	271.1	517.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C5-425AXSP08	180.6	281.5	215.3	242	-	180.6	280.5	214.9	241.5	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C5-432AXSP08	166.6	261.5	199.1	224.2	-	166.6	260.1	198.8	223.8	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C5-525AXSP08	201.6	310.5	238.8	267.5	-	201.7	309.2	238.2	266.7	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C5-532AXSP08	188.6	292.8	224.3	251.7	-	188.7	291.6	223.8	251	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C5-625AXSP08	216.4	329.6	254.8	284.8	539.8	216.4	328.3	254.5	283.6	535.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C5-632AXSP08	205.2	315.7	242.9	272.3	520.8	205.3	314.4	242.7	271.1	517.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C8-425AXSP08	180.6	281.5	215.3	242	-	180.6	280.5	214.9	241.5	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C8-432AXSP08	166.6	261.5	199.1	224.2	-	166.6	260.1	198.8	223.8	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C8-525AXSP08	201.6	310.5	238.8	267.5	-	201.7	309.2	238.2	266.7	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C8-532AXSP08	188.6	292.8	224.3	251.7	-	188.7	291.6	223.8	251	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C8-625AXSP08	216.4	329.6	254.8	284.8	539.8	216.4	328.3	254.5	283.6	535.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C8-632AXSP08	205.2	315.7	242.9	272.3	520.8	205.3	314.4	242.7	271.1	517.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C9-425AXSP08	180.6	281.5	215.3	242	-	180.6	280.5	214.9	241.5	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C9-432AXSP08	166.6	261.5	199.1	224.2	-	166.6	260.1	198.8	223.8	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550C9-525AXSP08	201.6	310.5	238.8	267.5	-	201.7	309.2	238.2	266.7	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C9-532AXSP08	188.6	292.8	224.3	251.7	-	188.7	291.6	223.8	251	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550C9-625AXSP08	216.4	329.6	254.8	284.8	539.8	216.4	328.3	254.5	283.6	535.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550C9-632AXSP08	205.2	315.7	242.9	272.3	520.8	205.3	314.4	242.7	271.1	517.8	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K2-425AXSP08	172.8	269	205.8	231.1	-	172.8	268	205.4	230.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K2-432AXSP08	159.8	250.3	190.9	214.8	-	159.9	249.4	190.6	214.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K2-525AXSP08	192.1	295.2	227.1	254.6	-	192.2	294	226.8	253.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K2-532AXSP08	180.2	279.1	214.2	240.2	464.6	180.1	278	213.7	239.6	461.9	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K2-625AXSP08	205.6	312.7	242	270.4	510.8	205.5	311.3	241.6	269.2	507.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K2-632AXSP08	195.1	300	231.5	259	494.8	195.4	298.6	230.8	258.1	491.2	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K3-425AXSP08	172.8	269	205.8	231.1	-	172.8	268	205.4	230.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K3-432AXSP08	159.8	250.3	190.9	214.8	-	159.9	249.4	190.6	214.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K3-525AXSP08	192.1	295.2	227.1	254.6	-	192.2	294	226.8	253.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K3-532AXSP08	180.2	279.1	214.2	240.2	464.6	180.1	278	213.7	239.6	461.9	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K3-625AXSP08	205.6	312.7	242	270.4	510.8	205.5	311.3	241.6	269.2	507.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K3-632AXSP08	195.1	300	231.5	259	494.8	195.4	298.6	230.8	258.1	491.2	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K4-425AXSP08	172.8	269	205.8	231.1	-	172.8	268	205.4	230.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K4-432AXSP08	159.8	250.3	190.9	214.8	-	159.9	249.4	190.6	214.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K4-525AXSP08	192.1	295.2	227.1	254.6	-	192.2	294	226.8	253.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K4-532AXSP08	180.2	279.1	214.2	240.2	464.6	180.1	278	213.7	239.6	461.9	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K4-625AXSP08	205.6	312.7	242	270.4	510.8	205.5	311.3	241.6	269.2	507.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K4-632AXSP08	195.1	300	231.5	259	494.8	195.4	298.6	230.8	258.1	491.2	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K5-425AXSP08	172.8	269	205.8	231.1	-	172.8	268	205.4	230.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K5-432AXSP08	159.8	250.3	190.9	214.8	-	159.9	249.4	190.6	214.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K5-525AXSP08	192.1	295.2	227.1	254.6	-	192.2	294	226.8	253.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K5-532AXSP08	180.2	279.1	214.2	240.2	464.6	180.1	278	213.7	239.6	461.9	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K5-625AXSP08	205.6	312.7	242	270.4	510.8	205.5	311.3	241.6	269.2	507.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K5-632AXSP08	195.1	300	231.5	259	494.8	195.4	298.6	230.8	258.1	491.2	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K8-425AXSP08	172.8	269	205.8	231.1	-	172.8	268	205.4	230.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K8-432AXSP08	159.8	250.3	190.9	214.8	-	159.9	249.4	190.6	214.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K8-525AXSP08	192.1	295.2	227.1	254.6	-	192.2	294	226.8	253.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K8-532AXSP08	180.2	279.1	214.2	240.2	464.6	180.1	278	213.7	239.6	461.9	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB550K8-625AXSP08	205.6	312.7	242	270.4	510.8	205.5	311.3	241.6	269.2	507.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K8-632AXSP08	195.1	300	231.5	259	494.8	195.4	298.6	230.8	258.1	491.2	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB550K9-425AXSP08	172.8	269	205.8	231.1	-	172.8	268	205.4	230.7	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB550K9-432AXSP08	159.8	250.3	190.9	214.8	-	159.9	249.4	190.6	214.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15																			

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PB750C8-525AXSP08	212.7	328.4	252.1	282.5	-	212.9	327.2	251.9	282.3	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750C8-532AXSP08	199.4	309.7	237	266.6	-	199.6	308.9	236.9	265.9	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750C8-625AXSP08	227.9	347.3	268.4	299.8	-	228	346.7	268.3	299.6	-	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750C8-632AXSP08	216.6	333.4	256.5	287.2	551.5	216.7	332.1	256.2	286.5	548.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750C9-425AXSP08	191	298.8	227.9	256.4	-	191.4	297.7	227.9	255.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750C9-432AXSP08	176.4	277.4	211	237.7	-	176.5	276.4	210.9	237.4	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750C9-525AXSP08	212.7	328.4	252.1	282.5	-	212.9	327.2	251.9	282.3	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750C9-532AXSP08	199.4	309.7	237	266.6	-	199.6	308.9	236.9	265.9	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750C9-625AXSP08	227.9	347.3	268.4	299.8	-	228	346.7	268.3	299.6	-	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750C9-632AXSP08	216.6	333.4	256.5	287.2	551.5	216.7	332.1	256.2	286.5	548.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K2-425AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K2-432AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K2-525AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K2-532AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K2-625AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K2-632AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K3-425AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K3-432AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K3-525AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K3-625AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K3-632AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K4-425AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K4-432AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K4-525AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K4-532AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K4-625AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K4-632AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K5-425AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K5-432AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K5-525AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K5-625AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K5-632AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K6-425AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K6-432AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K6-525AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K6-625AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K6-632AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K7-425AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K7-432AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K7-525AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K7-625AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K7-632AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K8-425AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K8-625AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K8-632AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K9-425AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K9-432AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K9-525AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K9-625AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K9-632AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K10-425AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K10-432AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K10-525AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K10-625AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K10-632AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K11-425AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K11-432AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K11-525AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K11-625AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K11-632AXSP08	205.6	316.9	243.6	272.9	-	205.6	315.6	243.2	272.5	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K12-425AXSP08	192.6	299.6	229.2	257.7	-	193.1	298.3	229.1	257	-	282	18.6	3"	225	16	2"	338	26.2	3"
EAW-VD15S3PB750K12-432AXSP08	220.2	335.6	259.3	289.9	549.7	220.6	334.5	259.1	289.3	546.6	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K12-525AXSP08	209.2	322	248	277.7	532.2	209.4	320.6	247.6	276.7	528.3	338	19.3	3"	270	12.7	3"	406	27	3"
EAW-VD15S3PB750K12-625AXSP08	184.9	288.6	220.4	247.9	-	185.2	287.5	220.4	247.3	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K12-632AXSP08	171	268.3	204.6	230.3	-	171.3	267.9	204.3	229.9	-	225	21.9	2"	180	14.4	2"	270	25.4	3"
EAW-VD15S3PB750K13-425AXSP08	205.6	316.9	243.6																

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PI400B3-432AXSP08	171.7	264.7	203.3	228.1	-	170.7	262.3	202	226.3	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400B3-525AXSP08	205.5	310.6	240.9	268.5	-	204.2	307.6	239.2	266.5	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400B3-532AXSP08	193.3	294.7	227.6	254.3	-	192.1	291.7	226	252.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400B3-625AXSP08	219.9	328.3	256.4	284.7	528.2	218.5	325.2	254.3	282.3	522.8	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400B3-632AXSP08	209.5	316.1	245.5	273.5	513.7	208.4	313.3	243.7	271.4	508	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400C3-425AXSP08	189.8	290.7	224.1	250.5	-	188.7	288.1	222.2	248.6	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400C3-432AXSP08	175.4	270.7	208	233.1	-	174.5	268.4	206.3	231.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400C3-525AXSP08	211	319.2	247.8	276.2	-	209.9	316.4	245.9	273.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400C3-532AXSP08	198.3	302.1	233.5	261	-	197	299.4	231.7	258.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400C3-625AXSP08	226.8	338.8	264.5	294	546.6	225.5	335.3	262.4	291.4	540	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400C3-632AXSP08	215.4	325.2	252.4	281.2	528.8	214.2	321.8	250.5	279	522.7	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400C9-425AXSP08	189.8	290.7	224.1	250.5	-	188.7	288.1	222.2	248.6	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400C9-432AXSP08	175.4	270.7	208	233.1	-	174.5	268.4	206.3	231.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400C9-525AXSP08	211	319.2	247.8	276.2	-	209.9	316.4	245.9	273.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400C9-532AXSP08	198.3	302.1	233.5	261	-	197	299.4	231.7	258.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400C9-625AXSP08	226.8	338.8	264.5	294	546.6	225.5	335.3	262.4	291.4	540	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400C9-632AXSP08	215.4	325.2	252.4	281.2	528.8	214.2	321.8	250.5	279	522.7	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400K3-425AXSP08	182.6	279.7	215.6	241.2	-	181.6	276.9	214.2	239.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400K3-432AXSP08	169.4	261	200.5	225	-	168.6	258.9	199.2	223.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400K3-525AXSP08	202.8	306.4	237.7	264.9	-	201.7	303.3	235.9	262.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400K3-532AXSP08	190.7	290.6	224.5	250.8	-	189.8	288	222.9	248.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400K3-625AXSP08	217.3	324.3	253.4	281.3	522.4	216.1	321	251.4	278.7	516.1	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400K3-632AXSP08	206.8	311.8	242.3	269.9	506.7	205.6	309	240.4	267.7	500.8	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400K9-425AXSP08	182.6	279.7	215.6	241.2	-	181.6	276.9	214.2	239.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400K9-432AXSP08	169.4	261	200.5	225	-	168.6	258.9	199.2	223.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400K9-525AXSP08	202.8	306.4	237.7	264.9	-	201.7	303.3	235.9	262.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400K9-532AXSP08	190.7	290.6	224.5	250.8	-	189.8	288	222.9	248.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400K9-625AXSP08	217.3	324.3	253.4	281.3	522.4	216.1	321	251.4	278.7	516.1	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400K9-632AXSP08	206.8	311.8	242.3	269.9	506.7	205.6	309	240.4	267.7	500.8	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400K9-632AXSP08	186.3	285.1	220	246.1	-	185.3	282.8	218.6	244.1	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400R3-432AXSP08	172.8	266.5	204.6	229.6	-	172.1	264.5	203.4	227.8	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI400R3-525AXSP08	206.7	312.6	242.7	270.5	-	205.8	309.9	240.6	268.2	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400R3-532AXSP08	194.5	296.6	229	255.9	-	193.6	294	227.4	254	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI400R3-625AXSP08	221.7	330.9	258.5	287	533.2	220.5	327.7	256.2	284.5	527	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI400R3-632AXSP08	211	318.5	247.3	275.5	517.6	209.7	313.5	245.5	273.1	511.3	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550B3-425AXSP06	195.8	303.6	232.4	261.1	-	195.4	301.4	231.6	259.7	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550B3-432AXSP08	187.9	290.6	223.1	250.3	-	187.3	288.6	221.9	248.5	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI550B3-525AXSP08	226.1	342.8	265.9	296.6	-	225.2	340.2	263.9	294.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550B3-532AXSP08	212.3	324.5	250.6	280.3	-	211.3	322.1	248.7	278.1	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C2-425AXSP08	242.8	363.7	283.2	315	-	241.6	360.7	281.5	312.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C2-432AXSP08	231	349.1	270.8	301.9	-	229.7	346.3	269	299.9	563.9	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C2-425AXSP06	204.3	317.5	243.1	273.3	-	203.9	315.2	242.1	271.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C2-432AXSP06	188.1	294	224.6	252.5	-	187.6	292.1	223.5	251.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C2-525AXSP08	237.8	361.3	279.5	312.3	-	236.5	358.3	277.6	309.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C2-532AXSP08	222	340.6	262.2	293.5	-	220.8	337.2	260.5	291.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C2-625AXSP08	256.7	385.1	299.9	333.7	-	255.1	381.4	297.7	330.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C2-632AXSP08	242.6	367.7	284.9	317.8	-	241.5	364.6	282.9	315.5	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C3-425AXSP06	204.3	317.5	243.1	273.3	-	203.9	315.2	242.1	271.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C3-432AXSP06	188.1	294	224.6	252.5	-	187.6	292.1	223.5	251.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C3-525AXSP08	237.8	361.3	279.5	312.3	-	236.5	358.3	277.6	309.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C3-532AXSP08	222	340.6	262.2	293.5	-	220.8	337.2	260.5	291.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C3-625AXSP08	256.7	385.1	299.9	333.7	-	255.1	381.4	297.7	330.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C3-632AXSP08	242.6	367.7	284.9	317.8	-	241.5	364.6	282.9	315.5	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C4-425AXSP06	204.3	317.5	243.1	273.3	-	203.9	315.2	242.1	271.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C4-432AXSP06	188.1	294	224.6	252.5	-	187.6	292.1	223.5	251.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C4-525AXSP08	237.8	361.3	279.5	312.3	-	236.5	358.3	277.6	309.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C4-532AXSP08	222	340.6	262.2	293.5	-	220.8	337.2	260.5	291.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C4-625AXSP08	256.7	385.1	299.9	333.7	-	255.1	381.4	297.7	330.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C4-632AXSP08	242.6	367.7	284.9	317.8	-	241.5	364.6	282.9	315.5	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C5-425AXSP06	204.3	317.5	243.1	273.3	-	203.9	315.2	242.1	271.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C5-432AXSP06	188.1	294	224.6	252.5	-	187.6	292.1	223.5	251.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550C5-525AXSP08	237.8	361.3	279.5	312.3	-	236.5	358.3	277.6	309.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C5-532AXSP08	222	340.6	262.2	293.5	-	220.8	337.2	260.5	291.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550C5-625AXSP08	256.7	385.1	299.9	333.7	-	255.1	381.4	297.7	330.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550C5-632AXSP08	242.6	367.7	284.9	317.8	-	241.5	364.6	282.9	315.5	-	338								

EAW-VD15S3PI550K8-425AXSP06	196.1	304.1	233.2	261.5	-	195.7	302	232	260.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550K8-432AXSP08	188.6	291.7	223.4	250.7	-	187.6	289.2	222.3	249.4	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI550K8-525AXSP08	227.2	344.5	266.9	297.7	-	225.9	341.3	264.7	295.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550K8-532AXSP08	212.7	325.6	251.1	280.8	-	211.7	323.1	249.5	279	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550K8-625AXSP08	244	365.6	284.9	317	-	242.9	362.3	283.1	314.5	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550K8-632AXSP08	231.8	350.3	271.8	303	-	230.4	347.4	269.9	300.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550K9-425AXSP06	196.1	304.1	233.2	261.5	-	195.7	302	232	260.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550K9-432AXSP08	188.6	291.7	223.4	250.7	-	187.6	289.2	222.3	249.4	-	225	27	2"	180	17.8	2"	270	32.6	3"
EAW-VD15S3PI550K9-525AXSP08	227.2	344.5	266.9	297.7	-	225.9	341.3	264.7	295.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550K9-532AXSP08	212.7	325.6	251.1	280.8	-	211.7	323.1	249.5	279	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550K9-625AXSP08	244	365.6	284.9	317	-	242.9	362.3	283.1	314.5	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550K9-632AXSP08	231.8	350.3	271.8	303	-	230.4	347.4	269.9	300.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550K9-425AXSP06	201.2	312.5	239.4	269	-	200.9	310.4	238.2	267.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550R3-432AXSP06	185.8	290.7	221.7	249.7	487.2	185.4	288.9	220.8	248.1	483.2	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI550R3-525AXSP08	233.3	354.1	274.1	305.8	-	232.1	351	272.4	303.9	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550R3-532AXSP08	218.7	334.7	257.8	288.5	-	217.7	332.2	256.3	286.7	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI550R3-625AXSP08	250.7	375.9	292.8	325.8	-	249.4	372.8	291.1	323.5	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI550R3-632AXSP08	237.9	360.5	279.5	311.6	-	236.7	357.2	277.7	309.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C2-425AXSP06	218.7	340.7	260.5	292.7	-	218.6	338.7	259.5	291.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C2-432AXSP06	201.3	315.6	240.7	270.9	-	201	313.9	239.9	269.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C2-525AXSP06	247.4	380	292.8	327.7	-	246.9	377.6	291.4	326.1	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750C2-532AXSP08	237.8	364.8	281	314.8	-	236.5	362.3	279.6	312.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750C3-625AXSP08	274.1	412.6	320.8	357.2	-	272.9	409.4	318.6	354.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C3-632AXSP08	259.3	394.1	305.1	340.6	-	258.2	391.4	303.1	338.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C3-625AXSP06	218.7	340.7	260.5	292.7	-	218.6	338.7	259.5	291.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C3-432AXSP06	201.3	315.6	240.7	270.9	-	201	313.9	239.9	269.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C3-525AXSP06	247.4	380	292.8	327.7	-	246.9	377.6	291.4	326.1	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750C3-532AXSP08	237.8	364.8	281	314.8	-	236.5	362.3	279.6	312.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750C3-625AXSP08	274.1	412.6	320.8	357.2	-	272.9	409.4	318.6	354.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C3-632AXSP08	259.3	394.1	305.1	340.6	-	258.2	391.4	303.1	338.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C4-425AXSP06	218.7	340.7	260.5	292.7	-	218.6	338.7	259.5	291.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C4-432AXSP06	201.3	315.6	240.7	270.9	-	201	313.9	239.9	269.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C4-525AXSP06	247.4	380	292.8	327.7	-	246.9	377.6	291.4	326.1	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750C4-532AXSP08	237.8	364.8	281	314.8	-	236.5	362.3	279.6	312.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750C4-625AXSP08	274.1	412.6	320.8	357.2	-	272.9	409.4	318.6	354.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C4-632AXSP08	259.3	394.1	305.1	340.6	-	258.2	391.4	303.1	338.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C5-425AXSP06	218.7	340.7	260.5	292.7	-	218.6	338.7	259.5	291.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C5-432AXSP06	201.3	315.6	240.7	270.9	-	201	313.9	239.9	269.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C5-525AXSP06	247.4	380	292.8	327.7	-	246.9	377.6	291.4	326.1	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750C5-532AXSP08	237.8	364.8	281	314.8	-	236.5	362.3	279.6	312.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750C5-625AXSP08	274.1	412.6	320.8	357.2	-	272.9	409.4	318.6	354.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C5-632AXSP08	259.3	394.1	305.1	340.6	-	258.2	391.4	303.1	338.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C8-425AXSP06	218.7	340.7	260.5	292.7	-	218.6	338.7	259.5	291.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C8-432AXSP06	201.3	315.6	240.7	270.9	-	201	313.9	239.9	269.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C8-525AXSP06	247.4	380	292.8	327.7	-	246.9	377.6	291.4	326.1	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750C8-532AXSP08	237.8	364.8	281	314.8	-	236.5	362.3	279.6	312.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750C8-625AXSP08	274.1	412.6	320.8	357.2	-	272.9	409.4	318.6	354.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C8-632AXSP08	259.3	394.1	305.1	340.6	-	258.2	391.4	303.1	338.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750C9-425AXSP06	218.7	340.7	260.5	292.7	-	218.6	338.7	259.5	291.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C9-432AXSP06	201.3	315.6	240.7	270.9	-	201	313.9	239.9	269.4	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750C9-525AXSP06	247.4	380	292.8	327.7	-	246.9	377.6	291.4	326.1	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750C9-625AXSP08	237.8	364.8	281	314.8	-	236.5	362.3	279.6	312.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750C9-632AXSP08	274.1	412.6	320.8	357.2	-	272.9	409.4	318.6	354.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750K2-425AXSP06	211.5	329.4	251.8	283.2	-	211.4	327.5	251.2	282	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750K2-432AXSP06	195.2	305.5	233.3	262.5	-	195.1	303.9	232.2	261.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750K2-525AXSP06	238.6	366.6	282.4	315.9	604.9	238.5	364.1	281.3	314.7	599.2	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750K2-532AXSP08	229.7	352.4	271.8	303.9	-	228.9	350	270	302.2	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750K2-625AXSP08	264.1	397	308.5	343.5	-	263	394	307	341.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750K2-632AXSP08	250.5	380.2	294.3	328.8	-	249.3	377	292.6	326.4	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750K3-425AXSP06	211.5	329.4	251.8	283.2	-	211.4	327.5	251.2	282	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750K3-432AXSP06	195.2	305.5	233.3	262.5	-	195.1	303.9	232.2	261.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S3PI750K3-525AXSP06	238.6	366.6	282.4	315.9	604.9	238.5	364.1	281.3	314.7	599.2	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S3PI750K3-532AXSP08	229.7	352.4	271.8	303.9	-	228.9	350	270	302.2	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S3PI750K3-625AXSP08	264.1	397	308.5	343.5	-	263	394	307	341.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750K3-632AXSP08	250.5	380.2	294.3	328.8	-	249.3	377	292.6	326.4	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S3PI750K4-425AXSP06	211.																		

EAW-VD1553PK370C2-632AXSP08	195	297.5	230.1	257.1	487.2	194.5	295.5	229.2	255.7	482.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370C4-425AXSP08	172.2	266.2	204.3	229.4	-	172	264.5	203.4	227.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370C4-432AXSP08	159.4	248.1	189.7	213.4	-	159	246.6	188.9	212.1	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370C4-525AXSP08	191.8	292.2	226	252.6	-	191.3	290.3	224.9	251	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370C4-532AXSP08	179.8	276.8	213.1	238.5	458.1	179.4	274.9	212	237.2	453.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370C4-625AXSP08	205.2	309.6	240.7	267.9	502.7	204.6	307.5	239.5	266.5	497.8	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370C4-632AXSP08	195	297.5	230.1	257.1	487.2	194.5	295.5	229.2	255.7	482.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370C5-425AXSP08	172.2	266.2	204.3	229.4	-	172	264.5	203.4	227.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370C5-432AXSP08	159.4	248.1	189.7	213.4	-	159	246.6	188.9	212.1	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370C5-525AXSP08	191.8	292.2	226	252.6	-	191.3	290.3	224.9	251	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370C5-532AXSP08	179.8	276.8	213.1	238.5	458.1	179.4	274.9	212	237.2	453.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370C5-625AXSP08	205.2	309.6	240.7	267.9	502.7	204.6	307.5	239.5	266.5	497.8	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370C5-632AXSP08	195	297.5	230.1	257.1	487.2	194.5	295.5	229.2	255.7	482.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370C8-425AXSP08	172.2	266.2	204.3	229.4	-	172	264.5	203.4	227.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370C8-432AXSP08	159.4	248.1	189.7	213.4	-	159	246.6	188.9	212.1	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370C8-525AXSP08	191.8	292.2	226	252.6	-	191.3	290.3	224.9	251	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370C8-532AXSP08	179.8	276.8	213.1	238.5	458.1	179.4	274.9	212	237.2	453.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370C8-625AXSP08	205.2	309.6	240.7	267.9	502.7	204.6	307.5	239.5	266.5	497.8	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370C8-632AXSP08	195	297.5	230.1	257.1	487.2	194.5	295.5	229.2	255.7	482.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K2-425AXSP08	166	256	196.9	220.5	-	165.7	254.4	195.9	219.4	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K2-432AXSP08	154	239.2	183.2	205.6	-	153.6	237.8	182.1	204.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K2-525AXSP08	184.2	280.6	217	242.4	459.8	183.7	278.7	215.9	241.1	455.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K2-532AXSP08	173	266.2	204.9	229.6	440.1	172.6	264.3	203.8	228.3	435.7	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K2-625AXSP08	196.9	296.7	231	257	481	196.3	294.7	229.7	255.5	476.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K2-632AXSP08	187.7	285.8	221.4	246.8	467.1	187.1	283.8	220.1	245.4	462.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K4-425AXSP08	166	256	196.9	220.5	-	165.7	254.4	195.9	219.4	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K4-432AXSP08	154	239.2	183.2	205.6	-	153.6	237.8	182.1	204.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K4-525AXSP08	184.2	280.6	217	242.4	459.8	183.7	278.7	215.9	241.1	455.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K4-532AXSP08	173	266.2	204.9	229.6	440.1	172.6	264.3	203.8	228.3	435.7	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K4-625AXSP08	196.9	296.7	231	257	481	196.3	294.7	229.7	255.5	476.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K4-632AXSP08	187.7	285.8	221.4	246.8	467.1	187.1	283.8	220.1	245.4	462.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K5-425AXSP08	166	256	196.9	220.5	-	165.7	254.4	195.9	219.4	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K5-432AXSP08	154	239.2	183.2	205.6	-	153.6	237.8	182.1	204.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K5-525AXSP08	184.2	280.6	217	242.4	459.8	183.7	278.7	215.9	241.1	455.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K5-532AXSP08	173	266.2	204.9	229.6	440.1	172.6	264.3	203.8	228.3	435.7	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K5-625AXSP08	196.9	296.7	231	257	481	196.3	294.7	229.7	255.5	476.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K5-632AXSP08	187.7	285.8	221.4	246.8	467.1	187.1	283.8	220.1	245.4	462.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K8-425AXSP08	166	256	196.9	220.5	-	165.7	254.4	195.9	219.4	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K8-432AXSP08	154	239.2	183.2	205.6	-	153.6	237.8	182.1	204.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK370K8-525AXSP08	184.2	280.6	217	242.4	459.8	183.7	278.7	215.9	241.1	455.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K8-532AXSP08	173	266.2	204.9	229.6	440.1	172.6	264.3	203.8	228.3	435.7	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK370K8-625AXSP08	196.9	296.7	231	257	481	196.3	294.7	229.7	255.5	476.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK370K8-632AXSP08	187.7	285.8	221.4	246.8	467.1	187.1	283.8	220.1	245.4	462.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400B3-425AXSP08	167.8	259	199	223	-	167.6	257.5	198.2	222.1	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400B3-432AXSP08	155.6	241.9	185.5	208.2	-	155.3	240.5	184.4	206.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400B3-525AXSP08	186	283.5	219.2	244.9	464.6	185.6	281.7	218.1	243.3	460.5	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK400B3-532AXSP08	175	269.1	207.4	232	445	174.5	267.4	206.4	230.9	440.9	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK400B3-625AXSP08	198.1	298.9	232.6	258.8	484.6	197.7	296.9	231.3	257.3	480.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400B3-632AXSP08	189.2	288.6	223.2	249.2	471.9	188.7	286.4	222.4	247.9	467.6	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400C3-425AXSP08	172.2	266.2	204.3	229.4	-	172	264.5	203.4	227.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400C3-432AXSP08	159.4	248.1	189.7	213.4	-	159	246.6	188.9	212.1	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400C3-525AXSP08	191.8	292.2	226	252.6	-	191.3	290.3	224.9	251	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK400C3-532AXSP08	179.8	276.8	213.1	238.5	458.1	179.4	274.9	212	237.2	453.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK400C3-625AXSP08	205.2	309.6	240.7	267.9	502.7	204.6	307.5	239.5	266.5	497.8	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400C3-632AXSP08	195	297.5	230.1	257.1	487.2	194.5	295.5	229.2	255.7	482.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400C9-425AXSP08	172.2	266.2	204.3	229.4	-	172	264.5	203.4	227.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400C9-432AXSP08	159.4	248.1	189.7	213.4	-	159	246.6	188.9	212.1	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400C9-525AXSP08	191.8	292.2	226	252.6	-	191.3	290.3	224.9	251	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK400C9-532AXSP08	179.8	276.8	213.1	238.5	458.1	179.4	274.9	212	237.2	453.6	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK400C9-625AXSP08	205.2	309.6	240.7	267.9	502.7	204.6	307.5	239.5	266.5	497.8	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400C9-632AXSP08	195	297.5	230.1	257.1	487.2	194.5	295.5	229.2	255.7	482.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK400K3-425AXSP08	166	256	196.9	220.5	-	165.7	254.4	195.9	219.4	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400K3-432AXSP08	154	239.2	183.2	205.6	-	153.6	237.8	182.1	204.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK400K3-525AXSP08	184.2	280.6	217	242.4	459.8	183.7	278.7	215.9	241.1	455.6	282	20.4	3"	225					

EAW-VD15S3PK550C4-625AXSP08	231.4	350.8	272	303	-	231	348.4	270.9	301.7	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C4-632AXSP08	219.3	335.5	258.6	289.3	551.7	219	333	257.5	287.9	546.9	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C5-425AXSP08	192.6	298.4	228.8	257	-	192.2	296.8	228	255.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550C5-432AXSP08	177.4	277.2	211.7	238.1	-	177	275.4	210.6	236.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550C5-525AXSP08	214.9	329.5	254	284.2	-	214.6	327.7	252.9	283	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550C5-532AXSP08	201.2	310.4	238.3	267.6	-	200.7	308.5	237.3	265.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550C5-625AXSP08	231.4	350.8	272	303	-	231	348.4	270.9	301.7	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C5-632AXSP08	219.3	335.5	258.6	289.3	551.7	219	333	257.5	287.9	546.9	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C8-425AXSP08	192.6	298.4	228.8	257	-	192.2	296.8	228	255.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550C8-432AXSP08	177.4	277.2	211.7	238.1	-	177	275.4	210.6	236.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550C8-525AXSP08	214.9	329.5	254	284.2	-	214.6	327.7	252.9	283	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550C8-532AXSP08	201.2	310.4	238.3	267.6	-	200.7	308.5	237.3	265.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550C8-625AXSP08	231.4	350.8	272	303	-	231	348.4	270.9	301.7	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C8-632AXSP08	219.3	335.5	258.6	289.3	551.7	219	333	257.5	287.9	546.9	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C9-425AXSP08	192.6	298.4	228.8	257	-	192.2	296.8	228	255.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550C9-432AXSP08	177.4	277.2	211.7	238.1	-	177	275.4	210.6	236.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550C9-525AXSP08	214.9	329.5	254	284.2	-	214.6	327.7	252.9	283	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550C9-532AXSP08	201.2	310.4	238.3	267.6	-	200.7	308.5	237.3	265.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550C9-625AXSP08	231.4	350.8	272	303	-	231	348.4	270.9	301.7	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550C9-632AXSP08	219.3	335.5	258.6	289.3	551.7	219	333	257.5	287.9	546.9	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K2-425AXSP08	184.2	285.2	218.7	245.4	-	183.8	283.7	218	244.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K2-432AXSP08	170.2	265.6	202.8	228.4	-	170	264.3	202.2	227.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K2-525AXSP08	205	313.7	241.8	270.5	-	204.5	311.6	240.9	269.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K2-532AXSP08	192.3	296.4	228	255.4	-	192.1	294.7	227.1	254.3	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K2-632AXSP08	219.9	332.4	258.1	287.4	540.5	219.2	330.1	257	286.1	536.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K2-632AXSP08	208.7	319	246.3	275.4	523.4	208.4	316.8	245.3	274.1	519	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K3-425AXSP08	184.2	285.2	218.7	245.4	-	183.8	283.7	218	244.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K3-432AXSP08	170.2	265.6	202.8	228.4	-	170	264.3	202.2	227.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K3-525AXSP08	205	313.7	241.8	270.5	-	204.5	311.6	240.9	269.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K3-532AXSP08	192.3	296.4	228	255.4	-	192.1	294.7	227.1	254.3	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K3-625AXSP08	219.9	332.4	258.1	287.4	540.5	219.2	330.1	257	286.1	536.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K3-632AXSP08	208.7	319	246.3	275.4	523.4	208.4	316.8	245.3	274.1	519	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K4-425AXSP08	184.2	285.2	218.7	245.4	-	183.8	283.7	218	244.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K4-432AXSP08	170.2	265.6	202.8	228.4	-	170	264.3	202.2	227.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K4-525AXSP08	205	313.7	241.8	270.5	-	204.5	311.6	240.9	269.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K4-532AXSP08	192.3	296.4	228	255.4	-	192.1	294.7	227.1	254.3	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K4-632AXSP08	219.9	332.4	258.1	287.4	540.5	219.2	330.1	257	286.1	536.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K4-632AXSP08	208.7	319	246.3	275.4	523.4	208.4	316.8	245.3	274.1	519	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K5-425AXSP08	184.2	285.2	218.7	245.4	-	183.8	283.7	218	244.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K5-432AXSP08	170.2	265.6	202.8	228.4	-	170	264.3	202.2	227.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K5-525AXSP08	205	313.7	241.8	270.5	-	204.5	311.6	240.9	269.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K5-532AXSP08	192.3	296.4	228	255.4	-	192.1	294.7	227.1	254.3	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K5-625AXSP08	219.9	332.4	258.1	287.4	540.5	219.2	330.1	257	286.1	536.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K5-632AXSP08	208.7	319	246.3	275.4	523.4	208.4	316.8	245.3	274.1	519	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K8-425AXSP08	184.2	285.2	218.7	245.4	-	183.8	283.7	218	244.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K8-432AXSP08	170.2	265.6	202.8	228.4	-	170	264.3	202.2	227.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K8-525AXSP08	205	313.7	241.8	270.5	-	204.5	311.6	240.9	269.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K8-532AXSP08	192.3	296.4	228	255.4	-	192.1	294.7	227.1	254.3	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K8-632AXSP08	219.9	332.4	258.1	287.4	540.5	219.2	330.1	257	286.1	536.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K9-425AXSP08	208.7	319	246.3	275.4	523.4	208.4	316.8	245.3	274.1	519	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K9-432AXSP08	184.2	285.2	218.7	245.4	-	183.8	283.7	218	244.5	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K9-432AXSP08	170.2	265.6	202.8	228.4	-	170	264.3	202.2	227.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550K9-525AXSP08	205	313.7	241.8	270.5	-	204.5	311.6	240.9	269.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K9-525AXSP08	192.3	296.4	228	255.4	-	192.1	294.7	227.1	254.3	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550K9-625AXSP08	219.9	332.4	258.1	287.4	540.5	219.2	330.1	257	286.1	536.2	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550K9-632AXSP08	208.7	319	246.3	275.4	523.4	208.4	316.8	245.3	274.1	519	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550R3-425AXSP08	188.9	293	224.5	252	-	188.7	291.1	223.8	250.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550R3-425AXSP08	174.4	272.2	208	233.9	-	174.4	271	207.5	232.9	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK550R3-525AXSP08	210.2	321.5	248	277.4	-	209.8	319.9	247.1	276	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550R3-532AXSP08	197.1	304.3	233.9	262.1	-	196.8	302.8	232.7	260.7	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK550R3-625AXSP08	225.4	341	264.6	295	555.3	225.1	338.8	263.5	293.5	550.5	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK550R3-632AXSP08	214.2	327.3	252.5	282.4	537.2	213.6	325.1	251.6	281.2	533	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD15S3PK750C2-425AXSP06	195.8	307.8	234.2	264.1	-	196.4	306.8	234.3	263.6	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD15S3PK750C2-432AXSP08	188.6	294.9	225.2	253.3	-	188.4	293.9	224.6	252.4	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD15S3PK750C2-525AXSP08	228.1	350.1	269.7	302	-	227.8	348.7	269	300.8	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD15S3PK750C2-532AXSP08	213.6	330.5	253.6	284.5	-	213.4	328.6	252.5	283.3	-	282	20.4							

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1553PK750K2-532AXSP08	206.6	319.2	244.9	275	-	206.5	318	244.3	273.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K2-625AXSP08	236.2	358.3	277.7	309.9	-	236.1	356.3	276.5	308.5	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K2-632AXSP08	224.5	343.6	265.1	296.2	-	224.1	341.6	264	295.2	561.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K3-425AXSP06	189.5	297.7	226.8	255.2	-	190	296.7	226.6	254.8	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD1553PK750K3-432AXSP08	182.8	285.6	218.1	245.6	-	182.7	284.6	217.4	244.6	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750K3-525AXSP08	220.1	337.8	260.2	291.3	-	220.2	336	259.5	290	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K3-532AXSP08	206.6	319.2	244.9	275	-	206.5	318	244.3	273.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K3-625AXSP08	236.2	358.3	277.7	309.9	-	236.1	356.3	276.5	308.5	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K3-632AXSP08	224.5	343.6	265.1	296.2	-	224.1	341.6	264	295.2	561.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K4-425AXSP06	189.5	297.7	226.8	255.2	-	190	296.7	226.6	254.8	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD1553PK750K4-432AXSP08	182.8	285.6	218.1	245.6	-	182.7	284.6	217.4	244.6	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750K4-525AXSP08	220.1	337.8	260.2	291.3	-	220.2	336	259.5	290	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K4-532AXSP08	206.6	319.2	244.9	275	-	206.5	318	244.3	273.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K4-625AXSP08	236.2	358.3	277.7	309.9	-	236.1	356.3	276.5	308.5	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K4-632AXSP08	224.5	343.6	265.1	296.2	-	224.1	341.6	264	295.2	561.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K5-425AXSP06	189.5	297.7	226.8	255.2	-	190	296.7	226.6	254.8	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD1553PK750K5-432AXSP08	182.8	285.6	218.1	245.6	-	182.7	284.6	217.4	244.6	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750K5-525AXSP08	220.1	337.8	260.2	291.3	-	220.2	336	259.5	290	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K5-532AXSP08	206.6	319.2	244.9	275	-	206.5	318	244.3	273.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K5-625AXSP08	236.2	358.3	277.7	309.9	-	236.1	356.3	276.5	308.5	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K5-632AXSP08	224.5	343.6	265.1	296.2	-	224.1	341.6	264	295.2	561.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K8-425AXSP06	189.5	297.7	226.8	255.2	-	190	296.7	226.6	254.8	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD1553PK750K8-432AXSP08	182.8	285.6	218.1	245.6	-	182.7	284.6	217.4	244.6	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750K8-525AXSP08	220.1	337.8	260.2	291.3	-	220.2	336	259.5	290	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K8-625AXSP08	206.6	319.2	244.9	275	-	206.5	318	244.3	273.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K8-632AXSP08	224.5	343.6	265.1	296.2	-	224.1	341.6	264	295.2	561.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K9-425AXSP06	189.5	297.7	226.8	255.2	-	190	296.7	226.6	254.8	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD1553PK750K9-432AXSP08	182.8	285.6	218.1	245.6	-	182.7	284.6	217.4	244.6	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750K9-525AXSP08	220.1	337.8	260.2	291.3	-	220.2	336	259.5	290	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K9-532AXSP08	206.6	319.2	244.9	275	-	206.5	318	244.3	273.9	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750K9-625AXSP08	236.2	358.3	277.7	309.9	-	236.1	356.3	276.5	308.5	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750K9-632AXSP08	224.5	343.6	265.1	296.2	-	224.1	341.6	264	295.2	561.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750R3-425AXSP08	193.9	300.6	230.4	258.8	-	193.9	299.5	230	257.8	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750R3-432AXSP08	179.3	280.1	213.7	240.5	-	178.9	278.6	213	239.6	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD1553PK750R3-525AXSP08	215.3	330.1	254.4	284.8	-	215	328.3	253.7	283.5	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750R3-532AXSP08	202.1	312.3	239.8	268.8	-	201.9	310.6	239.2	268.1	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD1553PK750R3-625AXSP08	230.9	349.5	271	302.3	-	230.7	347.5	270.1	300.9	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553PK750R3-632AXSP08	219.6	335.4	259	289.7	551.7	219.2	333.9	258.2	288.3	547.7	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD1553ZB70C2-425AXSP08	186.8	288.8	221.8	248.7	479	186.1	286.3	220.6	246.9	474	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C2-432AXSP08	172.2	269.1	205.9	231.2	449	171.8	266.9	204.6	229.7	444.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C2-525AXSP08	205.3	314	242.6	271.3	514.9	204.6	311.6	241.1	269.3	509.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C2-532AXSP08	191.9	296.9	228	255.8	490.5	191.4	294.3	226.7	254.2	485.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C2-625AXSP12	229.9	342.3	267.7	297.2	-	228.2	338.8	265.2	294.5	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70C2-632AXSP12	218.4	328.7	255.6	284.8	-	216.9	325.2	253.6	282.1	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70C4-425AXSP08	186.8	288.8	221.8	248.7	479	186.1	286.3	220.6	246.9	474	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C4-432AXSP08	172.2	269.1	205.9	231.2	449	171.8	266.9	204.6	229.7	444.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C4-525AXSP08	205.3	314	242.6	271.3	514.9	204.6	311.6	241.1	269.3	509.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C4-532AXSP08	191.9	296.9	228	255.8	490.5	191.4	294.3	226.7	254.2	485.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C4-625AXSP12	229.9	342.3	267.7	297.2	-	228.2	338.8	265.2	294.5	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70C4-632AXSP12	218.4	328.7	255.6	284.8	-	216.9	325.2	253.6	282.1	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70C5-425AXSP08	186.8	288.8	221.8	248.7	479	186.1	286.3	220.6	246.9	474	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C5-432AXSP08	172.2	269.1	205.9	231.2	449	171.8	266.9	204.6	229.7	444.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C5-525AXSP08	205.3	314	242.6	271.3	514.9	204.6	311.6	241.1	269.3	509.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C5-532AXSP08	191.9	296.9	228	255.8	490.5	191.4	294.3	226.7	254.2	485.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C5-625AXSP12	229.9	342.3	267.7	297.2	-	228.2	338.8	265.2	294.5	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70C5-632AXSP12	218.4	328.7	255.6	284.8	-	216.9	325.2	253.6	282.1	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70C8-425AXSP08	186.8	288.8	221.8	248.7	479	186.1	286.3	220.6	246.9	474	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C8-432AXSP08	172.2	269.1	205.9	231.2	449	171.8	266.9	204.6	229.7	444.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70C8-525AXSP08	205.3	314	242.6	271.3	514.9	204.6	311.6	241.1	269.3	509.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70C8-532AXSP08	191.9	296.9	228	255.8	490.5	191.4	294.3	226.7	254.2	485.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB70K2-532AXSP12	190.9	290.5	224.8	250.8	-	189.7	287.6	222.8	248.8	-	248	27	3"	198	20.9	2"	298	37.9	3"
EAW-VD1553ZB70K2-625AXSP12	220.6	327.7	256.5	284.4	-	219	324.3	254.1	281.7	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70K2-632AXSP12	210	315.2	245.4	273.2	-	208.5	311.8	243.4	270.6	504.7	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB70K4-425AXSP08	179.9	277.6	213.5	239.2	459.9	179.2	275.7	212.4	237.6	455.3	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB70K4-432AXSP08	166.5	259.6	198.5	223.2	432.6	166.1													

EAW-VD1553ZB400C9-525AXSP08	205.3	314	242.6	271.3	514.9	204.6	311.6	241.1	269.3	509.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB400C9-532AXSP08	191.9	296.9	228	255.8	490.5	191.4	294.3	226.7	254.2	485.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB400C9-625AXSP12	229.9	342.3	267.7	297.2	-	228.2	338.8	265.2	294.5	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400C9-632AXSP12	218.4	328.7	255.6	284.8	-	216.9	325.2	253.6	282.1	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400K3-425AXSP08	179.9	277.6	213.5	239.2	459.9	179.2	275.7	212.4	237.6	455.3	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB400K3-432AXSP08	166.5	259.6	198.5	223.2	432.6	166.1	257.5	197.6	221.8	428.3	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB400K3-525AXSP08	197.1	301.4	232.8	260.3	493.3	196.4	298.8	231.4	258.4	488.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB400K3-532AXSP12	190.9	290.5	224.8	250.8	-	189.7	287.6	222.8	248.8	-	248	27	3"	198	20.9	2"	298	37.9	3"
EAW-VD1553ZB400K3-625AXSP12	220.6	327.7	256.5	284.4	-	219	324.3	254.1	281.7	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400K3-632AXSP12	210	315.2	245.4	273.2	-	208.5	311.8	243.4	270.6	504.7	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400K9-425AXSP08	179.9	277.6	213.5	239.2	459.9	179.2	275.7	212.4	237.6	455.3	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB400K9-432AXSP08	166.5	259.6	198.5	223.2	432.6	166.1	257.5	197.6	221.8	428.3	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB400K9-525AXSP08	197.1	301.4	232.8	260.3	493.3	196.4	298.8	231.4	258.4	488.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB400K9-532AXSP12	190.9	290.5	224.8	250.8	-	189.7	287.6	222.8	248.8	-	248	27	3"	198	20.9	2"	298	37.9	3"
EAW-VD1553ZB400K9-625AXSP12	220.6	327.7	256.5	284.4	-	219	324.3	254.1	281.7	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400K9-632AXSP12	210	315.2	245.4	273.2	-	208.5	311.8	243.4	270.6	504.7	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400R3-425AXSP08	183.5	283.4	217.8	244.1	469.8	182.9	281.5	216.7	242.5	465.2	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB400R3-432AXSP08	169.8	264.6	202.9	227.9	442.1	169.5	263	201.8	226.5	437.9	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB400R3-525AXSP08	200.9	307.5	237.7	265.5	504.1	200.3	304.9	236	263.9	498.6	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB400R3-532AXSP12	194.7	296.6	229.3	256.2	-	193.6	293.6	227.4	254	-	248	27	3"	198	20.9	2"	298	37.9	3"
EAW-VD1553ZB400R3-625AXSP12	224.7	334.5	261.7	290.2	-	223.2	331.1	259.4	287.6	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB400R3-632AXSP12	214.1	321.9	250.5	278.6	-	212.6	318.6	248.3	276.1	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB550B3-425AXSP08	200.5	310.6	238.3	267	-	200	308.3	236.9	265.8	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550B3-432AXSP08	185.2	289	220.8	248.3	483.6	184.6	287	220.1	247	479.3	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C3-425AXSP08	220.2	337.2	260.3	291	554.6	219.5	335.1	259.2	289.2	549.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550B3-532AXSP08	206.1	319	245.1	274.8	528.7	205.6	316.6	243.7	273.1	523.9	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550B3-625AXSP08	237.4	360	279.2	311.5	585.2	236.9	357.4	277.9	309.7	579.2	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550B3-632AXSP12	234.1	353	274.5	305.9	-	232.8	350.2	272.2	303.4	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD1553ZB550C2-425AXSP08	209.6	324.8	249.2	279.4	-	209	322.3	247.7	277.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C2-432AXSP08	193	301.3	230.2	259.1	505.2	192.4	299.2	229	257.6	500.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C2-525AXSP08	231.4	355.1	273.8	306.2	584.8	230.9	352.7	272.4	304.6	579.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C2-532AXSP08	215.7	334	256.6	287.4	554.4	215	331.8	255	285.9	549	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C2-625AXSP08	251	381.3	295.7	329.7	620.5	250.2	378.1	293.6	327.3	613.9	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C2-632AXSP08	236.9	363.6	280.5	313.9	596.9	236.3	360.5	279	311.7	591.1	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C3-425AXSP08	209.6	324.8	249.2	279.4	-	209	322.3	247.7	277.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C3-432AXSP08	193	301.3	230.2	259.1	505.2	192.4	299.2	229	257.6	500.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C3-525AXSP08	231.4	355.1	273.8	306.2	584.8	230.9	352.7	272.4	304.6	579.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C3-532AXSP08	215.7	334	256.6	287.4	554.4	215	331.8	255	285.9	549	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C3-625AXSP08	251	381.3	295.7	329.7	620.5	250.2	378.1	293.6	327.3	613.9	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C3-632AXSP08	236.9	363.6	280.5	313.9	596.9	236.3	360.5	279	311.7	591.1	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C4-425AXSP08	209.6	324.8	249.2	279.4	-	209	322.3	247.7	277.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C4-432AXSP08	193	301.3	230.2	259.1	505.2	192.4	299.2	229	257.6	500.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C4-525AXSP08	231.4	355.1	273.8	306.2	584.8	230.9	352.7	272.4	304.6	579.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C4-532AXSP08	215.7	334	256.6	287.4	554.4	215	331.8	255	285.9	549	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C4-625AXSP08	251	381.3	295.7	329.7	620.5	250.2	378.1	293.6	327.3	613.9	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C4-632AXSP08	236.9	363.6	280.5	313.9	596.9	236.3	360.5	279	311.7	591.1	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C5-425AXSP08	209.6	324.8	249.2	279.4	-	209	322.3	247.7	277.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C5-432AXSP08	193	301.3	230.2	259.1	505.2	192.4	299.2	229	257.6	500.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C5-432AXSP08	231.4	355.1	273.8	306.2	584.8	230.9	352.7	272.4	304.6	579.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C5-525AXSP08	215.7	334	256.6	287.4	554.4	215	331.8	255	285.9	549	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C5-532AXSP08	251	381.3	295.7	329.7	620.5	250.2	378.1	293.6	327.3	613.9	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C5-625AXSP08	236.9	363.6	280.5	313.9	596.9	236.3	360.5	279	311.7	591.1	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C5-632AXSP08	209.6	324.8	249.2	279.4	-	209	322.3	247.7	277.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C8-425AXSP08	193	301.3	230.2	259.1	505.2	192.4	299.2	229	257.6	500.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C8-432AXSP08	231.4	355.1	273.8	306.2	584.8	230.9	352.7	272.4	304.6	579.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C8-525AXSP08	215.7	334	256.6	287.4	554.4	215	331.8	255	285.9	549	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C8-532AXSP08	251	381.3	295.7	329.7	620.5	250.2	378.1	293.6	327.3	613.9	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C8-625AXSP08	236.9	363.6	280.5	313.9	596.9	236.3	360.5	279	311.7	591.1	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C8-632AXSP08	209.6	324.8	249.2	279.4	-	209	322.3	247.7	277.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C9-425AXSP08	193	301.3	230.2	259.1	505.2	192.4	299.2	229	257.6	500.5	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD1553ZB550C9-432AXSP08	231.4	355.1	273.8	306.2	584.8	230.9	352.7	272.4	304.6	579.3	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C9-525AXSP08	215.7	334	256.6	287.4	554.4	215	331.8	255	285.9	549	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD1553ZB550C9-532AXSP08	251	381.3	295.7	329.7	620.5	250.2	378.1	293.6	327.3	613.9	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD1553ZB550C9-625AXSP0																			

EAW-VD15S3ZB550R3-432AXSP08	190.7	297.5	227.4	255.8	498.4	190.2	295.6	226.4	254.6	494.2	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB550R3-525AXSP08	227.1	348.2	268.6	300.4	573.2	226.4	345.7	267	298.6	568.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB550R3-532AXSP08	212.3	328.4	252.5	283.2	544.9	211.8	326.5	251.1	281.5	540.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB550R3-625AXSP08	245.3	372.4	288.6	322.1	605.8	244.5	369.7	287.3	320.2	600.1	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB550R3-632AXSP12	241.6	364.6	283.2	315.3	-	240.2	361.2	281	312.8	-	304	27.6	3"	244	18.2	3"	365	38.7	3"
EAW-VD15S3ZB750C2-425AXSP08	224.3	348.9	266.9	299.6	-	224	346.7	265.7	298.2	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C2-432AXSP08	206.8	323.2	246.6	277.9	-	206.5	321.3	245.6	276.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C2-525AXSP08	247.9	380.9	293	328.5	-	247.4	378.5	292	326.8	-	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C2-532AXSP08	230.9	358.2	274.5	308.3	596.1	230.6	355.9	273.7	306.7	591.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C2-625AXSP08	268.5	408.2	316.1	353.1	666.8	267.7	405.5	314.8	351.1	660.7	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C2-632AXSP08	253.6	389.7	300.5	336.1	641.7	253	387.1	299.3	334.2	636.4	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C3-425AXSP08	224.3	348.9	266.9	299.6	-	224	346.7	265.7	298.2	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C3-432AXSP08	206.8	323.2	246.6	277.9	-	206.5	321.3	245.6	276.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C3-525AXSP08	247.9	380.9	293	328.5	-	247.4	378.5	292	326.8	-	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C3-532AXSP08	230.9	358.2	274.5	308.3	596.1	230.6	355.9	273.7	306.7	591.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C3-625AXSP08	268.5	408.2	316.1	353.1	666.8	267.7	405.5	314.8	351.1	660.7	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C3-632AXSP08	253.6	389.7	300.5	336.1	641.7	253	387.1	299.3	334.2	636.4	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C4-425AXSP08	224.3	348.9	266.9	299.6	-	224	346.7	265.7	298.2	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C4-432AXSP08	206.8	323.2	246.6	277.9	-	206.5	321.3	245.6	276.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C4-525AXSP08	247.9	380.9	293	328.5	-	247.4	378.5	292	326.8	-	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C4-532AXSP08	230.9	358.2	274.5	308.3	596.1	230.6	355.9	273.7	306.7	591.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C4-625AXSP08	268.5	408.2	316.1	353.1	666.8	267.7	405.5	314.8	351.1	660.7	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C4-632AXSP08	253.6	389.7	300.5	336.1	641.7	253	387.1	299.3	334.2	636.4	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C5-425AXSP08	224.3	348.9	266.9	299.6	-	224	346.7	265.7	298.2	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C5-432AXSP08	206.8	323.2	246.6	277.9	-	206.5	321.3	245.6	276.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C5-525AXSP08	247.9	380.9	293	328.5	-	247.4	378.5	292	326.8	-	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C5-532AXSP08	230.9	358.2	274.5	308.3	596.1	230.6	355.9	273.7	306.7	591.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C5-625AXSP08	268.5	408.2	316.1	353.1	666.8	267.7	405.5	314.8	351.1	660.7	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C5-632AXSP08	253.6	389.7	300.5	336.1	641.7	253	387.1	299.3	334.2	636.4	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C8-425AXSP08	224.3	348.9	266.9	299.6	-	224	346.7	265.7	298.2	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C8-432AXSP08	206.8	323.2	246.6	277.9	-	206.5	321.3	245.6	276.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C8-525AXSP08	247.9	380.9	293	328.5	-	247.4	378.5	292	326.8	-	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C8-532AXSP08	230.9	358.2	274.5	308.3	596.1	230.6	355.9	273.7	306.7	591.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C8-625AXSP08	268.5	408.2	316.1	353.1	666.8	267.7	405.5	314.8	351.1	660.7	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C8-632AXSP08	253.6	389.7	300.5	336.1	641.7	253	387.1	299.3	334.2	636.4	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C9-425AXSP08	224.3	348.9	266.9	299.6	-	224	346.7	265.7	298.2	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C9-432AXSP08	206.8	323.2	246.6	277.9	-	206.5	321.3	245.6	276.7	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750C9-425AXSP08	247.9	380.9	293	328.5	-	247.4	378.5	292	326.8	-	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C9-532AXSP08	230.9	358.2	274.5	308.3	596.1	230.6	355.9	273.7	306.7	591.1	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750C9-625AXSP08	268.5	408.2	316.1	353.1	666.8	267.7	405.5	314.8	351.1	660.7	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C9-632AXSP08	253.6	389.7	300.5	336.1	641.7	253	387.1	299.3	334.2	636.4	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750C9-625AXSP08	217.2	336.8	258	289.9	-	216.6	335.2	257.3	288.5	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K2-432AXSP08	200.2	313.4	239	269.2	-	200.3	311.7	238.2	268.1	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K2-532AXSP08	223.2	346.2	265.7	298.2	575.4	222.9	344	264.4	296.7	570.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K2-625AXSP08	258.4	392.9	304.5	339.6	640.5	258.1	390.4	303	337.9	635	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K2-632AXSP08	244.7	376	289.8	324.5	618.6	244.4	373.3	288.6	322.6	612.6	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K3-425AXSP08	217.2	336.8	258	289.9	-	216.6	335.2	257.3	288.5	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K3-432AXSP08	200.2	313.4	239	269.2	-	200.3	311.7	238.2	268.1	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K3-525AXSP08	239.1	367.4	283	316.6	605.6	238.9	364.9	281.9	314.9	600.6	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K3-532AXSP08	223.2	346.2	265.7	298.2	575.4	222.9	344	264.4	296.7	570.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K3-632AXSP08	258.4	392.9	304.5	339.6	640.5	258.1	390.4	303	337.9	635	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K3-625AXSP08	244.7	376	289.8	324.5	618.6	244.4	373.3	288.6	322.6	612.6	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K4-432AXSP08	200.2	313.4	239	269.2	-	200.3	311.7	238.2	268.1	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K4-525AXSP08	239.1	367.4	283	316.6	605.6	238.9	364.9	281.9	314.9	600.6	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K4-625AXSP08	223.2	346.2	265.7	298.2	575.4	222.9	344	264.4	296.7	570.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K4-632AXSP08	258.4	392.9	304.5	339.6	640.5	258.1	390.4	303	337.9	635	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K4-625AXSP08	244.7	376	289.8	324.5	618.6	244.4	373.3	288.6	322.6	612.6	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K5-425AXSP08	217.2	336.8	258	289.9	-	216.6	335.2	257.3	288.5	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K5-432AXSP08	200.2	313.4	239	269.2	-	200.3	311.7	238.2	268.1	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K5-525AXSP08	239.1	367.4	283	316.6	605.6	238.9	364.9	281.9	314.9	600.6	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K5-532AXSP08	223.2	346.2	265.7	298.2	575.4	222.9	344	264.4	296.7	570.7	372	19.8	3"	298	13	3"	446	27.8	3"
EAW-VD15S3ZB750K5-625AXSP08	258.4	392.9	304.5	339.6	640.5	258.1	390.4	303	337.9	635	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K5-632AXSP08	244.7	376	289.8	324.5	618.6	244.4	373.3	288.6	322.6	612.6	451	21	3"	361	13.8	3"	541	25.9	4"
EAW-VD15S3ZB750K8-425AXSP08	217.2	336.8	258	289.9	-	216.6	335.2	257.3	288.5	-	304	18.9	3"	244	12.5	3"	365	26.6	3"
EAW-VD15S3ZB750K8-432AXSP08	200.2	3																	

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1553ZK370C5-425AXSP08	196.6	302.4	232.9	260.5	499.1	195.9	299.5	231	258.7	493.5	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370C5-432AXSP08	181.9	281.9	216.3	242.7	468.5	181.1	279.3	214.7	240.8	463.4	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370C5-525AXSP08	216.3	329	254.7	284.3	537.4	215.3	325.7	252.8	281.8	530.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370C5-532AXSP08	202.4	310.6	239.4	268	511.4	201.2	307.9	237.8	266	505.5	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370C5-625AXSP08	233.4	351.2	273.6	304.5	567.1	232.1	347.7	271.2	301.8	559.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK370C5-632AXSP12	229.6	343.4	267.9	297.8	-	227.6	339.7	265	294.6	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370C8-425AXSP08	196.6	302.4	232.9	260.5	499.1	195.9	299.5	231	258.7	493.5	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370C8-432AXSP08	181.9	281.9	216.3	242.7	468.5	181.1	279.3	214.7	240.8	463.4	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370C8-525AXSP08	216.3	329	254.7	284.3	537.4	215.3	325.7	252.8	281.8	530.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370C8-532AXSP08	202.4	310.6	239.4	268	511.4	201.2	307.9	237.8	266	505.5	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370C8-625AXSP08	233.4	351.2	273.6	304.5	567.1	232.1	347.7	271.2	301.8	559.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK370C8-632AXSP12	229.6	343.4	267.9	297.8	-	227.6	339.7	265	294.6	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K2-425AXSP08	189.6	291.1	224.5	250.9	480	188.7	288.4	222.7	248.9	474.8	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K2-432AXSP08	175.7	271.9	208.9	234.2	452	174.9	269.8	207.3	232.4	447.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K2-525AXSP08	207.7	315.6	244.6	272.9	515	206.8	312.5	242.8	270.5	508.7	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K2-532AXSP08	195	299.3	230.7	258.1	491.7	194	296.4	229.2	255.9	486.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K2-625AXSP12	231.5	342.6	268.5	297.5	-	229.6	338.3	265.7	294.5	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K2-632AXSP12	220.5	329.4	257.2	285.8	-	218.7	325.6	254.5	282.8	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K4-425AXSP08	189.6	291.1	224.5	250.9	480	188.7	288.4	222.7	248.9	474.8	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K4-432AXSP08	175.7	271.9	208.9	234.2	452	174.9	269.8	207.3	232.4	447.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K4-525AXSP08	207.7	315.6	244.6	272.9	515	206.8	312.5	242.8	270.5	508.7	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K4-532AXSP08	195	299.3	230.7	258.1	491.7	194	296.4	229.2	255.9	486.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K5-625AXSP12	231.5	342.6	268.5	297.5	-	229.6	338.3	265.7	294.5	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K5-632AXSP12	220.5	329.4	257.2	285.8	-	218.7	325.6	254.5	282.8	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K4-425AXSP08	189.6	291.1	224.5	250.9	480	188.7	288.4	222.7	248.9	474.8	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K4-432AXSP08	175.7	271.9	208.9	234.2	452	174.9	269.8	207.3	232.4	447.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K5-432AXSP08	207.7	315.6	244.6	272.9	515	206.8	312.5	242.8	270.5	508.7	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K5-532AXSP08	195	299.3	230.7	258.1	491.7	194	296.4	229.2	255.9	486.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K5-625AXSP12	231.5	342.6	268.5	297.5	-	229.6	338.3	265.7	294.5	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K5-632AXSP12	220.5	329.4	257.2	285.8	-	218.7	325.6	254.5	282.8	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K8-425AXSP08	189.6	291.1	224.5	250.9	480	188.7	288.4	222.7	248.9	474.8	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K8-432AXSP08	175.7	271.9	208.9	234.2	452	174.9	269.8	207.3	232.4	447.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK370K8-525AXSP08	207.7	315.6	244.6	272.9	515	206.8	312.5	242.8	270.5	508.7	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K8-532AXSP08	195	299.3	230.7	258.1	491.7	194	296.4	229.2	255.9	486.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK370K5-625AXSP12	231.5	342.6	268.5	297.5	-	229.6	338.3	265.7	294.5	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK370K8-632AXSP12	220.5	329.4	257.2	285.8	-	218.7	325.6	254.5	282.8	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK400B3-425AXSP08	192.3	295.1	227.4	254.6	487.3	191.4	292.8	226	252.6	482.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400B3-432AXSP08	178	275.7	211.7	237.4	458.5	177.3	273.2	210.2	235.6	453.5	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400B3-525AXSP08	210.7	320.2	248.1	276.8	522.7	209.8	317.1	246.3	274.5	516.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400B3-532AXSP08	197.5	303.3	234.1	261.8	499.2	196.8	300.5	232.2	259.7	493.7	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400B3-625AXSP08	226.9	341.1	265.6	295.6	550	225.7	337.8	263.6	293	542.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK400B3-632AXSP12	223.6	334.3	260.9	290	-	221.8	330.4	258.2	287	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK400C3-425AXSP08	196.6	302.4	232.9	260.5	499.1	195.9	299.5	231	258.7	493.5	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400C3-432AXSP08	181.9	281.9	216.3	242.7	468.5	181.1	279.3	214.7	240.8	463.4	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400C3-525AXSP08	216.3	329	254.7	284.3	537.4	215.3	325.7	252.8	281.8	530.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400C3-532AXSP08	202.4	310.6	239.4	268	511.4	201.2	307.9	237.8	266	505.5	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400C3-625AXSP08	233.4	351.2	273.6	304.5	567.1	232.1	347.7	271.2	301.8	559.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK400C3-632AXSP12	229.6	343.4	267.9	297.8	-	227.6	339.7	265	294.6	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK400C9-425AXSP08	196.6	302.4	232.9	260.5	499.1	195.9	299.5	231	258.7	493.5	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400C9-432AXSP08	181.9	281.9	216.3	242.7	468.5	181.1	279.3	214.7	240.8	463.4	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400C9-525AXSP08	216.3	329	254.7	284.3	537.4	215.3	325.7	252.8	281.8	530.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400C9-532AXSP08	202.4	310.6	239.4	268	511.4	201.2	307.9	237.8	266	505.5	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400C9-625AXSP08	233.4	351.2	273.6	304.5	567.1	232.1	347.7	271.2	301.8	559.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK400C9-632AXSP12	229.6	343.4	267.9	297.8	-	227.6	339.7	265	294.6	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK400K3-425AXSP08	189.6	291.1	224.5	250.9	480	188.7	288.4	222.7	248.9	474.8	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400K3-432AXSP08	175.7	271.9	208.9	234.2	452	174.9	269.8	207.3	232.4	447.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400K3-525AXSP08	207.7	315.6	244.6	272.9	515	206.8	312.5	242.8	270.5	508.7	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400K3-532AXSP08	195	299.3	230.7	258.1	491.7	194	296.4	229.2	255.9	486.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK400K3-625AXSP12	231.5	342.6	268.5	297.5	-	229.6	338.3	265.7	294.5	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK400K3-632AXSP12	220.5	329.4	257.2	285.8	-	218.7	325.6	254.5	282.8	-	304	30.2	3"	244	19.9	3"	365	42.3	3"
EAW-VD1553ZK400K9-425AXSP08	189.6	291.1	224.5	250.9	480	188.7	288.4	222.7	248.9	474.8	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400K9-432AXSP08	175.7	271.9	208.9	234.2	452	174.9	269.8	207.3	232.4	447.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK400K9-525AXSP08	207.7	315.6	244.6	272.9	515	206.8	312.5	242.8	270.5	508.7	372								

EAW-VD1553ZK550C5-632AXSP08	250.1	381.6	295.1	329.5	623.9	249	377.9	293	326.7	617	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550C8-425AXSP08	221.2	341	261.9	293.8	-	220.3	337.9	260.4	291.6	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550C8-432AXSP08	203.5	316.4	242.1	272.1	-	202.9	313.7	240.9	270.1	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550C8-525AXSP08	244.7	372.7	287.9	321.8	611.8	243.4	369.1	286	319.1	604.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550C8-532AXSP08	227.7	350.7	269.7	302.3	579.3	226.6	347.5	268.1	299.9	573	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550C8-625AXSP08	265.2	399.8	311.1	346.1	648.4	263.7	396.1	308.5	343.3	640.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550C8-632AXSP08	250.1	381.6	295.1	329.5	623.9	249	377.9	293	326.7	617	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550C9-425AXSP08	221.2	341	261.9	293.8	-	220.3	337.9	260.4	291.6	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550C9-432AXSP08	203.5	316.4	242.1	272.1	-	202.9	313.7	240.9	270.1	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550C9-525AXSP08	244.7	372.7	287.9	321.8	611.8	243.4	369.1	286	319.1	604.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550C9-532AXSP08	227.7	350.7	269.7	302.3	579.3	226.6	347.5	268.1	299.9	573	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550C9-625AXSP08	265.2	399.8	311.1	346.1	648.4	263.7	396.1	308.5	343.3	640.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550C9-632AXSP08	250.1	381.6	295.1	329.5	623.9	249	377.9	293	326.7	617	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K2-425AXSP08	212.4	326.8	251.4	281.9	-	211.7	324.6	250.1	279.9	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K2-432AXSP08	196.2	304.8	233.6	261.9	508	195.7	302.4	232.2	260.3	503.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K2-525AXSP08	233.7	355.8	275.3	307.5	582.8	232.5	352.6	273.2	305.1	576.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K2-532AXSP08	218.5	335.9	258.7	289.8	555	217.6	333.5	257.3	287.7	548.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K2-625AXSP08	252.3	380.3	295.8	329.5	615.5	251.2	376.9	293.9	326.9	608.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K2-632AXSP08	239.3	364	281.7	314.9	594.5	238	361.1	279.9	312.4	588.3	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K3-425AXSP08	212.4	326.8	251.4	281.9	-	211.7	324.6	250.1	279.9	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K3-432AXSP08	196.2	304.8	233.6	261.9	508	195.7	302.4	232.2	260.3	503.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K3-525AXSP08	233.7	355.8	275.3	307.5	582.8	232.5	352.6	273.2	305.1	576.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K3-532AXSP08	218.5	335.9	258.7	289.8	555	217.6	333.5	257.3	287.7	548.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K3-625AXSP08	252.3	380.3	295.8	329.5	615.5	251.2	376.9	293.9	326.9	608.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K3-632AXSP08	239.3	364	281.7	314.9	594.5	238	361.1	279.9	312.4	588.3	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K4-425AXSP08	212.4	326.8	251.4	281.9	-	211.7	324.6	250.1	279.9	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K4-432AXSP08	196.2	304.8	233.6	261.9	508	195.7	302.4	232.2	260.3	503.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K4-525AXSP08	233.7	355.8	275.3	307.5	582.8	232.5	352.6	273.2	305.1	576.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K4-532AXSP08	218.5	335.9	258.7	289.8	555	217.6	333.5	257.3	287.7	548.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K4-625AXSP08	252.3	380.3	295.8	329.5	615.5	251.2	376.9	293.9	326.9	608.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K4-632AXSP08	239.3	364	281.7	314.9	594.5	238	361.1	279.9	312.4	588.3	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K5-425AXSP08	212.4	326.8	251.4	281.9	-	211.7	324.6	250.1	279.9	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K5-432AXSP08	196.2	304.8	233.6	261.9	508	195.7	302.4	232.2	260.3	503.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K5-525AXSP08	233.7	355.8	275.3	307.5	582.8	232.5	352.6	273.2	305.1	576.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K5-532AXSP08	218.5	335.9	258.7	289.8	555	217.6	333.5	257.3	287.7	548.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K5-625AXSP08	252.3	380.3	295.8	329.5	615.5	251.2	376.9	293.9	326.9	608.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K5-632AXSP08	239.3	364	281.7	314.9	594.5	238	361.1	279.9	312.4	588.3	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K8-425AXSP08	212.4	326.8	251.4	281.9	-	211.7	324.6	250.1	279.9	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K8-432AXSP08	196.2	304.8	233.6	261.9	508	195.7	302.4	232.2	260.3	503.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K8-525AXSP08	233.7	355.8	275.3	307.5	582.8	232.5	352.6	273.2	305.1	576.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K8-532AXSP08	218.5	335.9	258.7	289.8	555	217.6	333.5	257.3	287.7	548.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K8-625AXSP08	252.3	380.3	295.8	329.5	615.5	251.2	376.9	293.9	326.9	608.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K8-632AXSP08	239.3	364	281.7	314.9	594.5	238	361.1	279.9	312.4	588.3	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K9-425AXSP08	212.4	326.8	251.4	281.9	-	211.7	324.6	250.1	279.9	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K9-432AXSP08	196.2	304.8	233.6	261.9	508	195.7	302.4	232.2	260.3	503.1	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550K9-525AXSP08	233.7	355.8	275.3	307.5	582.8	232.5	352.6	273.2	305.1	576.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K9-532AXSP08	218.5	335.9	258.7	289.8	555	217.6	333.5	257.3	287.7	548.6	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550K9-625AXSP08	252.3	380.3	295.8	329.5	615.5	251.2	376.9	293.9	326.9	608.6	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550K9-632AXSP08	239.3	364	281.7	314.9	594.5	238	361.1	279.9	312.4	588.3	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550R3-425AXSP08	218.4	336.4	258.5	289.9	-	217.6	333.7	257.2	288	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550R3-432AXSP08	201.9	313.1	240.1	269.3	-	201.1	310.8	238.7	267.7	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK550R3-525AXSP08	240.2	366.2	283.1	316.3	600.9	239.5	363	281.5	314	594.3	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550R3-532AXSP08	224.5	345.7	266.4	298	571.6	223.7	342.8	264.6	296	565.9	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK550R3-625AXSP08	259.7	391.8	304.6	339.3	634.4	258.7	388.4	302.7	336.7	627.5	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK550R3-632AXSP08	245.9	375	290.1	323.9	612.9	245.1	371.7	288.3	321.4	606	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750C2-425AXSP08	237.5	367.5	281.9	316.1	-	236.9	364.7	280.2	314.1	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750C2-432AXSP08	218.8	341	260.5	292.7	-	218.1	338	259.2	291	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750C2-525AXSP08	262.8	401.3	309.8	346.5	-	261.8	398.1	307.8	344.2	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750C2-532AXSP08	245.2	377.7	290.2	325.6	-	244	374.7	288.9	323.4	620.1	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750C2-625AXSP08	285	430.6	334.4	372.8	700.7	283.8	427.2	332.2	369.8	692.8	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750C2-632AXSP08	268.9	410.8	317.4	354.7	673.6	268.2	407.4	315.7	352.2	667.1	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750C3-425AXSP08	237.5	367.5	281.9	316.1	-	236.9	364.7	280.2	314.1	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750C3-432AXSP08	218.8	341	260.5	292.7	-	218.1	338	259.2	291	-	304	20.7	3"	244					

EAW-VD1553ZK750K3-625AXSP08	274.5	414.7	322	358.8	672.9	273.6	410.8	320.2	356.3	665.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K3-632AXSP08	259.8	396.4	306.6	342.5	649.3	258.7	393.1	304.5	340.1	642.4	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K4-425AXSP08	229.8	355	272.7	305.6	-	229.3	352.4	271.2	303.8	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K4-432AXSP08	212.5	330.6	252.9	284	-	211.9	328.4	251.7	282.5	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K4-525AXSP08	253.5	387.1	299.2	334.1	-	252.9	384.1	297.3	331.8	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K4-532AXSP08	237.1	365.3	281	314.6	604	236.4	362.4	279.3	312.6	598.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K4-625AXSP08	274.5	414.7	322	358.8	672.9	273.6	410.8	320.2	356.3	665.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K4-632AXSP08	259.8	396.4	306.6	342.5	649.3	258.7	393.1	304.5	340.1	642.4	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K5-425AXSP08	229.8	355	272.7	305.6	-	229.3	352.4	271.2	303.8	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K5-432AXSP08	212.5	330.6	252.9	284	-	211.9	328.4	251.7	282.5	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K5-525AXSP08	253.5	387.1	299.2	334.1	-	252.9	384.1	297.3	331.8	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K5-532AXSP08	237.1	365.3	281	314.6	604	236.4	362.4	279.3	312.6	598.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K5-625AXSP08	274.5	414.7	322	358.8	672.9	273.6	410.8	320.2	356.3	665.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K5-632AXSP08	259.8	396.4	306.6	342.5	649.3	258.7	393.1	304.5	340.1	642.4	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K8-425AXSP08	229.8	355	272.7	305.6	-	229.3	352.4	271.2	303.8	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K8-432AXSP08	212.5	330.6	252.9	284	-	211.9	328.4	251.7	282.5	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K8-525AXSP08	253.5	387.1	299.2	334.1	-	252.9	384.1	297.3	331.8	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K8-532AXSP08	237.1	365.3	281	314.6	604	236.4	362.4	279.3	312.6	598.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K8-625AXSP08	274.5	414.7	322	358.8	672.9	273.6	410.8	320.2	356.3	665.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K8-632AXSP08	259.8	396.4	306.6	342.5	649.3	258.7	393.1	304.5	340.1	642.4	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750K9-425AXSP08	229.8	355	272.7	305.6	-	229.3	352.4	271.2	303.8	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K9-432AXSP08	212.5	330.6	252.9	284	-	211.9	328.4	251.7	282.5	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750K9-525AXSP08	253.5	387.1	299.2	334.1	-	252.9	384.1	297.3	331.8	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750K9-532AXSP08	237.1	365.3	281	314.6	604	236.4	362.4	279.3	312.6	598.4	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750R3-525AXSP08	274.5	414.7	322	358.8	672.9	273.6	410.8	320.2	356.3	665.9	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750R3-632AXSP08	259.8	396.4	306.6	342.5	649.3	258.7	393.1	304.5	340.1	642.4	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750R3-625AXSP08	225.3	347.7	266.8	299.5	-	224.4	345.1	265.7	297.7	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750R3-432AXSP08	208.3	323.7	247.8	278.1	-	207.7	321.5	246.6	276.7	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD1553ZK750R3-525AXSP08	248.1	378.6	292.4	326.8	620.9	247.1	375.6	290.5	324.6	615.2	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750R3-532AXSP08	232	357.1	274.9	307.7	591	231.3	354.4	273.3	305.8	584.8	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD1553ZK750R3-625AXSP08	267.9	404.6	314.7	350.2	656.2	267.1	401.3	312.5	347.8	649.4	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1553ZK750R3-632AXSP08	254	387.1	299.6	334.6	633.9	252.9	383.9	298	332.3	627.1	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD1554PB370C2-425AXSP06	212.2	329.8	252.6	283.6	-	212	328.4	251.9	282.8	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C2-432AXSP06	196.1	307	234	263.7	-	196.2	305.7	233.4	262.5	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C2-525AXSP06	237.9	365.4	281.5	314.9	602.1	237.7	363.5	280.4	313.7	598.1	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD1554PB370C2-532AXSP08	230	352.8	271.7	304.2	-	229.5	350.4	270.7	302.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD1554PB370C2-625AXSP08	261.7	393.4	305.8	340.3	-	261.1	390.6	304.7	338.7	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C2-632AXSP08	249.6	378.8	293.2	327.2	-	248.8	376.2	292	325.3	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C4-425AXSP06	212.2	329.8	252.6	283.6	-	212	328.4	251.9	282.8	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C4-432AXSP06	196.1	307	234	263.7	-	196.2	305.7	233.4	262.5	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C4-525AXSP06	237.9	365.4	281.5	314.9	602.1	237.7	363.5	280.4	313.7	598.1	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD1554PB370C4-532AXSP08	230	352.8	271.7	304.2	-	229.5	350.4	270.7	302.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD1554PB370C4-625AXSP08	261.7	393.4	305.8	340.3	-	261.1	390.6	304.7	338.7	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C4-632AXSP08	249.6	378.8	293.2	327.2	-	248.8	376.2	292	325.3	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C5-425AXSP06	212.2	329.8	252.6	283.6	-	212	328.4	251.9	282.8	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C5-432AXSP06	196.1	307	234	263.7	-	196.2	305.7	233.4	262.5	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C5-525AXSP06	237.9	365.4	281.5	314.9	602.1	237.7	363.5	280.4	313.7	598.1	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD1554PB370C5-532AXSP08	230	352.8	271.7	304.2	-	229.5	350.4	270.7	302.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD1554PB370C5-625AXSP08	261.7	393.4	305.8	340.3	-	261.1	390.6	304.7	338.7	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C5-632AXSP08	249.6	378.8	293.2	327.2	-	248.8	376.2	292	325.3	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C8-425AXSP06	212.2	329.8	252.6	283.6	-	212	328.4	251.9	282.8	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C8-432AXSP06	196.1	307	234	263.7	-	196.2	305.7	233.4	262.5	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370C8-525AXSP06	237.9	365.4	281.5	314.9	602.1	237.7	363.5	280.4	313.7	598.1	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD1554PB370C8-532AXSP08	230	352.8	271.7	304.2	-	229.5	350.4	270.7	302.6	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD1554PB370C8-625AXSP08	261.7	393.4	305.8	340.3	-	261.1	390.6	304.7	338.7	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370C8-632AXSP08	249.6	378.8	293.2	327.2	-	248.8	376.2	292	325.3	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370K2-425AXSP06	204.3	317.5	243.1	273.2	-	204.4	316	242.3	271.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370K2-432AXSP06	189	296.1	225.7	254.2	-	188.9	294.3	225.1	253	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370K2-525AXSP08	235.4	357.9	276.9	309	-	234.6	355.4	275.4	307.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD1554PB370K2-532AXSP08	221.7	339.5	261.8	293	-	221.1	337.1	260.4	291.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD1554PB370K2-625AXSP08	251.9	377.8	294.3	327.5	-	251	375.2	292.6	325.6	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370K2-632AXSP08	240.3	364.2	282.3	314.8	-	239.5	361.6	280.6	312.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD1554PB370K4-425AXSP06	204.3	317.5	243.1	273.2	-	204.4	316	242.3	271.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370K4-432AXSP06	189	296.1	225.7	254.2	-	188.9	294.3	225.1	253	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD1554PB370K4-52																			

EAW-VD15S4PB400K3-532AXSP08	221.7	339.5	261.8	293	-	221.1	337.1	260.4	291.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S4PB400K3-625AXSP08	251.9	377.8	294.3	327.5	-	251	375.2	292.6	325.6	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB400K3-632AXSP08	240.3	364.2	282.3	314.8	-	239.5	361.6	280.6	312.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB400K9-425AXSP06	204.3	317.5	243.1	273.2	-	204.4	316	242.3	271.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB400K9-432AXSP06	189	296.1	225.7	254.2	-	188.9	294.3	225.1	253	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB400K9-525AXSP08	235.4	357.9	276.9	309	-	234.6	355.4	275.4	307.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S4PB400K9-532AXSP08	221.7	339.5	261.8	293	-	221.1	337.1	260.4	291.3	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S4PB400K9-625AXSP08	251.9	377.8	294.3	327.5	-	251	375.2	292.6	325.6	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB400K9-632AXSP08	240.3	364.2	282.3	314.8	-	239.5	361.6	280.6	312.9	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB400R3-425AXSP06	207.7	323.1	247.2	277.5	-	207.9	321.2	246.6	276.7	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB400R3-432AXSP06	192.4	301.1	229.7	258.8	-	192.3	299.9	222.2	257.7	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB400R3-525AXSP08	239.1	363.9	281.4	314.1	-	238.5	361.5	280	312.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S4PB400R3-532AXSP08	225.4	345.4	266.2	298	-	224.5	343.1	264.9	296.4	-	282	23.8	3"	225	19.4	2"	338	33.4	3"
EAW-VD15S4PB400R3-625AXSP08	255.7	384.2	299.2	332.5	-	254.9	381.2	297.6	330.7	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB400R3-632AXSP08	244.1	370.2	286.8	319.9	-	243.4	367.6	285.2	318.1	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550B3-425AXSP06	224.7	349.9	267.7	300.9	-	224.9	348.9	267.5	300	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550B3-432AXSP06	207.8	326.3	248.6	279.9	-	208	324.9	248.3	279.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550B3-525AXSP06	251.7	387	297.5	333.6	-	251.7	385.3	297.1	332.6	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550B3-532AXSP06	236.5	366.7	281.2	315.9	611.5	236.5	365.4	280.7	314.7	607.4	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550B3-625AXSP08	275.7	415.1	322.7	359.3	-	275.3	413.6	321.8	358.4	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550B3-632AXSP08	263.6	400.8	310.2	346.3	-	263.3	398.9	309.1	345.1	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550C2-425AXSP06	236.3	368.5	281.8	317	-	236.4	367.3	281.4	315.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C2-432AXSP06	217.5	341.7	260.1	293.1	-	217.6	340.6	259.6	292.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C2-525AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C2-532AXSP06	249.2	386.8	296.5	332.8	-	249	385.2	295.8	331.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C2-625AXSP06	287.7	438.4	339.3	378.7	717.9	287.7	436.6	338.4	377.7	713.3	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB550C2-632AXSP08	279.3	425.7	328.9	367.4	-	278.8	423.3	327.5	365.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550C3-425AXSP06	236.3	368.5	281.8	317	-	236.4	367.3	281.4	315.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C3-432AXSP06	217.5	341.7	260.1	293.1	-	217.6	340.6	259.6	292.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C3-525AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C3-532AXSP06	249.2	386.8	296.5	332.8	-	249	385.2	295.8	331.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C3-625AXSP06	287.7	438.4	339.3	378.7	717.9	287.7	436.6	338.4	377.7	713.3	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB550C3-632AXSP08	279.3	425.7	328.9	367.4	-	278.8	423.3	327.5	365.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550C4-425AXSP06	236.3	368.5	281.8	317	-	236.4	367.3	281.4	315.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C4-432AXSP06	217.5	341.7	260.1	293.1	-	217.6	340.6	259.6	292.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C4-525AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C4-532AXSP06	249.2	386.8	296.5	332.8	-	249	385.2	295.8	331.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C4-625AXSP06	287.7	438.4	339.3	378.7	717.9	287.7	436.6	338.4	377.7	713.3	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB550C4-632AXSP08	279.3	425.7	328.9	367.4	-	278.8	423.3	327.5	365.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550C5-425AXSP06	236.3	368.5	281.8	317	-	236.4	367.3	281.4	315.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C5-432AXSP06	217.5	341.7	260.1	293.1	-	217.6	340.6	259.6	292.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C5-432AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C5-525AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C5-532AXSP06	249.2	386.8	296.5	332.8	-	249	385.2	295.8	331.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C5-625AXSP06	287.7	438.4	339.3	378.7	717.9	287.7	436.6	338.4	377.7	713.3	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB550C5-632AXSP08	279.3	425.7	328.9	367.4	-	278.8	423.3	327.5	365.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550C8-425AXSP06	236.3	368.5	281.8	317	-	236.4	367.3	281.4	315.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C8-432AXSP06	217.5	341.7	260.1	293.1	-	217.6	340.6	259.6	292.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C8-525AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C8-532AXSP06	249.2	386.8	296.5	332.8	-	249	385.2	295.8	331.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C8-625AXSP06	287.7	438.4	339.3	378.7	717.9	287.7	436.6	338.4	377.7	713.3	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB550C8-632AXSP08	279.3	425.7	328.9	367.4	-	278.8	423.3	327.5	365.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550C9-425AXSP06	236.3	368.5	281.8	317	-	236.4	367.3	281.4	315.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C9-432AXSP06	217.5	341.7	260.1	293.1	-	217.6	340.6	259.6	292.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550C9-525AXSP06	266.7	410.4	315.9	353.9	-	266.4	408.8	315.1	353	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C9-532AXSP06	249.2	386.8	296.5	332.8	-	249	385.2	295.8	331.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550C9-625AXSP06	287.7	438.4	339.3	378.7	717.9	287.7	436.6	338.4	377.7	713.3	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB550C9-632AXSP08	279.3	425.7	328.9	367.4	-	278.8	423.3	327.5	365.8	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550K2-425AXSP06	225.7	352.3	269	302.9	-	226.2	350.6	268.6	301.8	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550K2-432AXSP06	208.7	327.7	249.6	281	-	208.9	326.1	249.2	280	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB550K2-525AXSP06	253.8	390.3	300.4	336.4	-	253.9	388.7	299.7	335.5	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550K2-532AXSP06	237.7	369.3	283.2	317.6	615.1	238	367.9	282.6	316.8	610.7	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB550K2-625AXSP08	279.6	421.6	327.6	364.9	-	278.9	419.2	326.1	363.2	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550K2-632AXSP08	266.2	404.9	312.9	349.8	-	265.3	402.5	311.9	348.1	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD15S4PB550K3-425AXSP06	225.7	352.3	269	302.9	-	226.2	350.6	268.6	301.8	-	293	18.3	3"	234	16.1	2"			

EAW-VD15S4PB750C2-525AXSP06	280.8	434	333.4	373.8	-	281.6	433.1	333.2	373	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C2-532AXSP06	263	409.6	313.2	351.9	-	263.3	408.6	313.1	351.6	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C2-625AXSP06	302.9	462.5	356.9	399.2	-	303.6	461	356.8	398.4	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C2-632AXSP06	287.8	443.3	340.9	381.8	733.5	288	442.2	340.6	381.4	729.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C3-425AXSP06	249.8	390.9	298.1	335.7	-	250.3	389.6	297.7	335.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C3-432AXSP06	230.1	362.2	275.8	310.6	-	230.6	361.1	275.4	310.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C3-525AXSP06	280.8	434	333.4	373.8	-	281.6	433.1	333.2	373	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C3-532AXSP06	263	409.6	313.2	351.9	-	263.3	408.6	313.1	351.6	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C3-625AXSP06	302.9	462.5	356.9	399.2	-	303.6	461	356.8	398.4	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C3-632AXSP06	287.8	443.3	340.9	381.8	733.5	288	442.2	340.6	381.4	729.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C4-425AXSP06	249.8	390.9	298.1	335.7	-	250.3	389.6	297.7	335.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C4-432AXSP06	230.1	362.2	275.8	310.6	-	230.6	361.1	275.4	310.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C4-525AXSP06	280.8	434	333.4	373.8	-	281.6	433.1	333.2	373	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C4-532AXSP06	263	409.6	313.2	351.9	-	263.3	408.6	313.1	351.6	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C4-625AXSP06	302.9	462.5	356.9	399.2	-	303.6	461	356.8	398.4	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C4-632AXSP06	287.8	443.3	340.9	381.8	733.5	288	442.2	340.6	381.4	729.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C5-425AXSP06	249.8	390.9	298.1	335.7	-	250.3	389.6	297.7	335.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C5-432AXSP06	230.1	362.2	275.8	310.6	-	230.6	361.1	275.4	310.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C5-525AXSP06	280.8	434	333.4	373.8	-	281.6	433.1	333.2	373	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C5-625AXSP06	302.9	462.5	356.9	399.2	-	303.6	461	356.8	398.4	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C5-632AXSP06	287.8	443.3	340.9	381.8	733.5	288	442.2	340.6	381.4	729.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C8-425AXSP06	249.8	390.9	298.1	335.7	-	250.3	389.6	297.7	335.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C8-432AXSP06	230.1	362.2	275.8	310.6	-	230.6	361.1	275.4	310.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C8-532AXSP06	280.8	434	333.4	373.8	-	281.6	433.1	333.2	373	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C8-632AXSP06	263	409.6	313.2	351.9	-	263.3	408.6	313.1	351.6	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C8-625AXSP06	302.9	462.5	356.9	399.2	-	303.6	461	356.8	398.4	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C8-632AXSP06	287.8	443.3	340.9	381.8	733.5	288	442.2	340.6	381.4	729.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C9-425AXSP06	249.8	390.9	298.1	335.7	-	250.3	389.6	297.7	335.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C9-432AXSP06	230.1	362.2	275.8	310.6	-	230.6	361.1	275.4	310.1	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750C9-525AXSP06	280.8	434	333.4	373.8	-	281.6	433.1	333.2	373	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C9-632AXSP06	263	409.6	313.2	351.9	-	263.3	408.6	313.1	351.6	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750C9-625AXSP06	302.9	462.5	356.9	399.2	-	303.6	461	356.8	398.4	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750C9-632AXSP06	287.8	443.3	340.9	381.8	733.5	288	442.2	340.6	381.4	729.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D2-425AXSP06	241.9	377.7	288.5	324.1	-	241.9	376.4	288	324	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D2-432AXSP06	223.1	351.1	267.2	301.1	-	223.6	350.1	267	300.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D2-532AXSP06	271.5	418.9	322.2	361.1	-	272	417.7	321.8	360	-	293	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D2-632AXSP06	254.5	395.6	303	340.2	-	254.8	394.6	302.8	339.8	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D2-625AXSP06	292.7	446.3	345.3	385.5	731.2	293.3	444.8	344.5	384.6	727	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D2-632AXSP06	278	428.2	329.6	369.1	707.7	278.4	426.8	329.1	367.9	703.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D3-425AXSP06	241.9	377.7	288.5	324.1	-	241.9	376.4	288	324	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D3-432AXSP06	223.1	351.1	267.2	301.1	-	223.6	350.1	267	300.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D3-532AXSP06	271.5	418.9	322.2	361.1	-	272	417.7	321.8	360	-	293	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D3-632AXSP06	254.5	395.6	303	340.2	-	254.8	394.6	302.8	339.8	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D3-625AXSP06	292.7	446.3	345.3	385.5	731.2	293.3	444.8	344.5	384.6	727	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D3-632AXSP06	278	428.2	329.6	369.1	707.7	278.4	426.8	329.1	367.9	703.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D4-425AXSP06	241.9	377.7	288.5	324.1	-	241.9	376.4	288	324	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D4-432AXSP06	223.1	351.1	267.2	301.1	-	223.6	350.1	267	300.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D4-532AXSP06	271.5	418.9	322.2	361.1	-	272	417.7	321.8	360	-	293	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D4-632AXSP06	254.5	395.6	303	340.2	-	254.8	394.6	302.8	339.8	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D4-625AXSP06	292.7	446.3	345.3	385.5	731.2	293.3	444.8	344.5	384.6	727	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D5-425AXSP06	241.9	377.7	288.5	324.1	-	241.9	376.4	288	324	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D5-432AXSP06	223.1	351.1	267.2	301.1	-	223.6	350.1	267	300.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D5-532AXSP06	271.5	418.9	322.2	361.1	-	272	417.7	321.8	360	-	293	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D5-632AXSP06	254.5	395.6	303	340.2	-	254.8	394.6	302.8	339.8	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D5-625AXSP06	292.7	446.3	345.3	385.5	731.2	293.3	444.8	344.5	384.6	727	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D5-632AXSP06	278	428.2	329.6	369.1	707.7	278.4	426.8	329.1	367.9	703.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D8-425AXSP06	241.9	377.7	288.5	324.1	-	241.9	376.4	288	324	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D8-432AXSP06	223.1	351.1	267.2	301.1	-	223.6	350.1	267	300.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D8-525AXSP06	271.5	418.9	322.2	361.1	-	272	417.7	321.8	360	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D8-532AXSP06	254.5	395.6	303	340.2	-	254.8	394.6	302.8	339.8	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D8-625AXSP06	292.7	446.3	345.3	385.5	731.2	293.3	444.8	344.5	384.6	727	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D8-632AXSP06	278	428.2	329.6	369.1	707.7	278.4	426.8	329.1	367.9	703.5	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD15S4PB750D9-425AXSP06	241.9	377.7	288.5	324.1	-	241.9	376.4	288	324	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D9-432AXSP06	223.1	351.1	267.2	301.1	-	223.6	350.1	267	300.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD15S4PB750D9-525AXSP06	271.5	418.9	322.2	361.1	-	272	417.7	321.8	360	-	293	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD15S4PB750D9-632AXSP06	254.5	395.6	303	340.2	-	254.8	394.6	302.8	339.8	-	372	19.2	3"</						

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S4PI370K2-432AXSP06	221.5	342	262.7	294.5	-	220.5	339.3	260.7	292.1	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K2-525AXSP06	268.5	405.4	314.8	350.8	-	266.8	401.8	312.4	347.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K2-532AXSP06	252.3	384.2	297.1	332	-	250.7	380.8	294.9	329	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K2-625AXSP06	289.4	431.9	337	374.6	695	287.3	427.5	334.4	371.2	686.6	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K2-632AXSP06	274.9	414.8	322.6	359.3	674	273.4	410.9	320.1	356	666.2	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K4-425AXSP06	239.2	366.5	282.5	316.2	-	237.9	363.5	280.7	313.6	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K4-432AXSP06	221.5	342	262.7	294.5	-	220.5	339.3	260.7	292.1	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K4-525AXSP06	268.5	405.4	314.8	350.8	-	266.8	401.8	312.4	347.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K4-532AXSP06	252.3	384.2	297.1	332	-	250.7	380.8	294.9	329	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K4-625AXSP06	289.4	431.9	337	374.6	695	287.3	427.5	334.4	371.2	686.6	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K4-632AXSP06	274.9	414.8	322.6	359.3	674	273.4	410.9	320.1	356	666.2	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K5-425AXSP06	239.2	366.5	282.5	316.2	-	237.9	363.5	280.7	313.6	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K5-432AXSP06	221.5	342	262.7	294.5	-	220.5	339.3	260.7	292.1	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K5-525AXSP06	268.5	405.4	314.8	350.8	-	266.8	401.8	312.4	347.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K5-532AXSP06	252.3	384.2	297.1	332	-	250.7	380.8	294.9	329	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K5-625AXSP06	289.4	431.9	337	374.6	695	287.3	427.5	334.4	371.2	686.6	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K5-632AXSP06	274.9	414.8	322.6	359.3	674	273.4	410.9	320.1	356	666.2	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K8-425AXSP06	239.2	366.5	282.5	316.2	-	237.9	363.5	280.7	313.6	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K8-432AXSP06	221.5	342	262.7	294.5	-	220.5	339.3	260.7	292.1	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI370K8-525AXSP06	268.5	405.4	314.8	350.8	-	266.8	401.8	312.4	347.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K8-532AXSP06	252.3	384.2	297.1	332	-	250.7	380.8	294.9	329	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI370K8-625AXSP06	289.4	431.9	337	374.6	695	287.3	427.5	334.4	371.2	686.6	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI370K8-632AXSP06	274.9	414.8	322.6	359.3	674	273.4	410.9	320.1	356	666.2	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400B3-425AXSP06	242.5	371.7	286.4	320.6	-	241.2	368.7	284.6	318	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400C3-425AXSP06	224.5	346.8	266.3	298.6	-	223.6	343.7	264.3	296.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400B3-525AXSP06	272	410.9	319	355.5	-	270.4	407.5	316.7	352.5	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400B3-532AXSP06	255.3	389.6	301.2	336.5	-	254.2	386.3	299.1	333.6	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400B3-625AXSP06	292.4	436.6	341	378.6	703.5	290.6	432.5	338.2	375.5	695.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400B3-632AXSP06	278.6	420.4	326.9	364.2	684.2	277.1	416.7	324.5	360.9	675.7	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400C3-425AXSP06	248.5	381.3	293.6	328.8	-	247.1	377.5	291.6	325.9	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400C3-432AXSP06	229.2	354.5	272	305	-	228.1	351.7	270.3	303	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400C3-525AXSP06	279.3	422.9	328	365.7	-	277.5	418.6	325.1	362.4	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400C3-532AXSP06	261.9	400	308.5	345.4	-	260.2	396.4	306.2	342.2	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400C3-625AXSP06	301.6	451.2	351.7	391.1	727.2	299.9	446.6	349	387.5	718.4	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400C3-632AXSP06	286.3	432.5	336.1	374.5	704.2	284.8	428.6	333	371	696.1	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400C9-425AXSP06	248.5	381.3	293.6	328.8	-	247.1	377.5	291.6	325.9	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400C9-432AXSP06	229.2	354.5	272	305	-	228.1	351.7	270.3	303	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400C9-525AXSP06	279.3	422.9	328	365.7	-	277.5	418.6	325.1	362.4	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400C9-532AXSP06	261.9	400	308.5	345.4	-	260.2	396.4	306.2	342.2	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400C9-625AXSP06	301.6	451.2	351.7	391.1	727.2	299.9	446.6	349	387.5	718.4	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400C9-632AXSP06	286.3	432.5	336.1	374.5	704.2	284.8	428.6	333	371	696.1	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400K3-425AXSP06	239.2	366.5	282.5	316.2	-	237.9	363.5	280.7	313.6	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400K3-432AXSP06	221.5	342	262.7	294.5	-	220.5	339.3	260.7	292.1	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400K3-525AXSP06	268.5	405.4	314.8	350.8	-	266.8	401.8	312.4	347.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400K3-532AXSP06	252.3	384.2	297.1	332	-	250.7	380.8	294.9	329	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400K3-625AXSP06	289.4	431.9	337	374.6	695	287.3	427.5	334.4	371.2	686.6	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400K3-632AXSP06	274.9	414.8	322.6	359.3	674	273.4	410.9	320.1	356	666.2	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400K9-425AXSP06	239.2	366.5	282.5	316.2	-	237.9	363.5	280.7	313.6	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400K9-432AXSP06	221.5	342	262.7	294.5	-	220.5	339.3	260.7	292.1	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400K9-525AXSP06	268.5	405.4	314.8	350.8	-	266.8	401.8	312.4	347.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400K9-532AXSP06	252.3	384.2	297.1	332	-	250.7	380.8	294.9	329	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400K9-625AXSP06	289.4	431.9	337	374.6	695	287.3	427.5	334.4	371.2	686.6	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400K9-632AXSP06	274.9	414.8	322.6	359.3	674	273.4	410.9	320.1	356	666.2	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400R3-425AXSP06	243.9	374.1	288.2	322.6	-	242.8	371.1	286.4	320.5	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400R3-432AXSP06	225.9	349.1	268	300.5	-	225	346	266	298.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI400R3-525AXSP06	273.7	414.1	320.9	357.7	-	272	410	318.6	355.1	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400R3-532AXSP06	257.3	392.1	303	338.7	-	255.8	388.8	301	336.3	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI400R3-625AXSP06	294.8	440.2	343.7	382.2	709.4	293.2	435.9	341.2	378.8	701.8	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI400R3-632AXSP06	280.6	423.6	328.9	366.4	688.5	278.8	419.3	326.4	363.6	680.9	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550B3-425AXSP04	259.7	406	310.5	348.7	676.8	259.7	403.2	309.3	347.3	670.8	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550B3-432AXSP06	245.9	380.5	292	327.3	-	244.7	378	290.1	325.6	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550B3-525AXSP06	299.2	454.1	351.5	392.2	-	297.7	450.7	349.4	389.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550B3-532AXSP06	280.8	429.5	331	370.3	-	279.5	426.4	329.1	368.1	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550B3-625AXSP06	322.9	483.8	377.1	419	-	321.3	479.8	374.4	416	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550B3-632AXSP06	307.1	464.8	360.1	402	-	305.4													

EAW-VD15S4PI550K2-425AXSP04	260.6	406.7	311.5	349.8	679	260.5	404.5	310.3	347.9	673	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550K2-432AXSP06	246.2	381.8	292.5	328.4	-	245.1	378.7	290.6	326.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550K2-525AXSP06	300.2	455.7	352.7	394.1	-	298.6	452.1	350.5	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K2-532AXSP06	281.3	430.4	332.2	371.6	-	280	427.1	330.1	368.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K2-625AXSP06	324.8	486.8	378.9	421.6	-	323	482.4	376.4	418.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K2-632AXSP06	308.1	466.5	361.8	403.4	-	306.4	462.1	358.9	400.1	752.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K3-425AXSP04	260.6	406.7	311.5	349.8	679	260.5	404.5	310.3	347.9	673	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550K3-432AXSP06	246.2	381.8	292.5	328.4	-	245.1	378.7	290.6	326.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550K3-525AXSP06	300.2	455.7	352.7	394.1	-	298.6	452.1	350.5	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K3-532AXSP06	281.3	430.4	332.2	371.6	-	280	427.1	330.1	368.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K3-625AXSP06	324.8	486.8	378.9	421.6	-	323	482.4	376.4	418.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K3-632AXSP06	308.1	466.5	361.8	403.4	-	306.4	462.1	358.9	400.1	752.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K4-425AXSP04	260.6	406.7	311.5	349.8	679	260.5	404.5	310.3	347.9	673	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550K4-432AXSP06	246.2	381.8	292.5	328.4	-	245.1	378.7	290.6	326.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550K4-525AXSP06	300.2	455.7	352.7	394.1	-	298.6	452.1	350.5	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K4-532AXSP06	281.3	430.4	332.2	371.6	-	280	427.1	330.1	368.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K4-625AXSP06	324.8	486.8	378.9	421.6	-	323	482.4	376.4	418.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K4-632AXSP06	308.1	466.5	361.8	403.4	-	306.4	462.1	358.9	400.1	752.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K8-425AXSP04	260.6	406.7	311.5	349.8	679	260.5	404.5	310.3	347.9	673	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550K8-432AXSP06	246.2	381.8	292.5	328.4	-	245.1	378.7	290.6	326.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550K5-525AXSP06	300.2	455.7	352.7	394.1	-	298.6	452.1	350.5	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K5-532AXSP06	281.3	430.4	332.2	371.6	-	280	427.1	330.1	368.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K5-625AXSP06	324.8	486.8	378.9	421.6	-	323	482.4	376.4	418.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K5-632AXSP06	308.1	466.5	361.8	403.4	-	306.4	462.1	358.9	400.1	752.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K8-425AXSP04	260.6	406.7	311.5	349.8	679	260.5	404.5	310.3	347.9	673	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550K8-432AXSP06	246.2	381.8	292.5	328.4	-	245.1	378.7	290.6	326.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550K8-525AXSP06	300.2	455.7	352.7	394.1	-	298.6	452.1	350.5	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K8-532AXSP06	281.3	430.4	332.2	371.6	-	280	427.1	330.1	368.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K8-625AXSP06	324.8	486.8	378.9	421.6	-	323	482.4	376.4	418.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K8-632AXSP06	308.1	466.5	361.8	403.4	-	306.4	462.1	358.9	400.1	752.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K9-425AXSP04	260.6	406.7	311.5	349.8	679	260.5	404.5	310.3	347.9	673	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550K9-432AXSP06	246.2	381.8	292.5	328.4	-	245.1	378.7	290.6	326.2	-	293	23.4	3"	234	19.5	2"	352	32.9	3"
EAW-VD15S4PI550K9-525AXSP06	300.2	455.7	352.7	394.1	-	298.6	452.1	350.5	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K9-532AXSP06	281.3	430.4	332.2	371.6	-	280	427.1	330.1	368.7	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550K9-625AXSP06	324.8	486.8	378.9	421.6	-	323	482.4	376.4	418.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550K9-632AXSP06	308.1	466.5	361.8	403.4	-	306.4	462.1	358.9	400.1	752.5	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550R3-425AXSP04	267.8	417.9	319.7	359.3	698.4	267.5	415.8	318.7	358	692.5	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550R3-432AXSP04	246.7	388.9	296.2	333.5	653.6	246.7	386.6	295.6	332.6	648.3	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI550R3-525AXSP06	308.3	468.4	362.8	404.9	-	307.2	464.9	360.6	401.8	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550R3-532AXSP06	288.8	442.3	341	381.7	-	287.5	439.1	339.1	378.8	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4PI550R3-625AXSP06	333.3	500.6	389.4	433.3	-	331.7	496.4	387.1	430.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI550R3-632AXSP06	316.7	479.4	371.5	414.4	-	315.1	475.6	369.2	411.6	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C2-425AXSP04	291.1	455.7	348	391.6	-	291.5	453	347.2	389.8	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C2-432AXSP04	267.8	422.3	321.6	361.9	711.3	268	420	320.5	360.5	705.7	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C2-525AXSP04	325.7	503.9	387.4	434.4	834.8	325.6	501.4	386.2	432.2	827.2	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C2-532AXSP04	303.2	474.6	363	407.7	791.1	303.3	471.6	361.9	406.3	784.6	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C2-625AXSP06	364.5	548.8	426.5	475	-	362.9	544.5	424.3	471.8	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C2-632AXSP06	344.7	524	405.7	452.8	-	343.7	520.4	403.5	450.3	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C3-425AXSP04	291.1	455.7	348	391.6	-	291.5	453	347.2	389.8	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C3-432AXSP04	267.8	422.3	321.6	361.9	711.3	268	420	320.5	360.5	705.7	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C3-525AXSP04	325.7	503.9	387.4	434.4	834.8	325.6	501.4	386.2	432.2	827.2	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C3-532AXSP04	303.2	474.6	363	407.7	791.1	303.3	471.6	361.9	406.3	784.6	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C3-625AXSP06	364.5	548.8	426.5	475	-	362.9	544.5	424.3	471.8	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C3-632AXSP06	344.7	524	405.7	452.8	-	343.7	520.4	403.5	450.3	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C4-425AXSP04	291.1	455.7	348	391.6	-	291.5	453	347.2	389.8	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C4-432AXSP04	267.8	422.3	321.6	361.9	711.3	268	420	320.5	360.5	705.7	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C4-525AXSP04	325.7	503.9	387.4	434.4	834.8	325.6	501.4	386.2	432.2	827.2	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C4-532AXSP04	303.2	474.6	363	407.7	791.1	303.3	471.6	361.9	406.3	784.6	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C4-625AXSP06	364.5	548.8	426.5	475	-	362.9	544.5	424.3	471.8	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C4-632AXSP06	344.7	524	405.7	452.8	-	343.7	520.4	403.5	450.3	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PI750C5-425AXSP04	291.1	455.7	348	391.6	-	291.5	453	347.2	389.8	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C5-432AXSP04	267.8	422.3	321.6	361.9	711.3	268	420	320.5	360.5	705.7	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4PI750C5-525AXSP04	325.7	503.9	387.4	434.4	834.8	325.6	501.4	386.2	432.2	827.2	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C5-532AXSP04	303.2	474.6	363	407.7	791.1	303.3	471.6	361.9	406.3	784.6	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4PI750C5-625AXSP06	364.5	548.8	426.																

EAW-VD15S4P1750K5-632AXSP06	333	505.6	391.8	437.2	-	331.5	502	389	434	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4P1750K8-425AXSP04	281.5	440.6	336.4	378.3	736.6	281.9	438	335.6	376.6	730.8	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4P1750K8-432AXSP04	259.5	408.8	311.7	351.3	688.7	259.6	407.3	310.7	350	683.5	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4P1750K8-525AXSP04	314.2	486.1	373.6	418.8	803.5	314	483.5	372.3	417.1	796.9	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4P1750K8-532AXSP06	303.8	466.4	358.9	402	-	302.7	462.6	357.2	399.3	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4P1750K8-625AXSP06	351.1	528.1	410.8	457.3	-	349.7	524.1	408.2	454.4	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4P1750K8-632AXSP06	333	505.6	391.8	437.2	-	331.5	502	389	434	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4P1750K9-425AXSP04	281.5	440.6	336.4	378.3	736.6	281.9	438	335.6	376.6	730.8	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4P1750K9-432AXSP04	259.5	408.8	311.7	351.3	688.7	259.6	407.3	310.7	350	683.5	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4P1750K9-525AXSP04	314.2	486.1	373.6	418.8	803.5	314	483.5	372.3	417.1	796.9	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4P1750K9-532AXSP06	303.8	466.4	358.9	402	-	302.7	462.6	357.2	399.3	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4P1750K9-625AXSP06	351.1	528.1	410.8	457.3	-	349.7	524.1	408.2	454.4	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4P1750K9-632AXSP06	333	505.6	391.8	437.2	-	331.5	502	389	434	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4P1750R3-425AXSP04	275.6	430.8	329.7	370.1	720.8	275.9	428.9	328.4	369	715.1	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4P1750R3-432AXSP04	254.2	400.9	305.5	344.2	674.8	254.5	398.8	304.5	342.9	669.7	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD15S4P1750R3-525AXSP04	307.1	475.3	365.6	409.6	785.1	306.9	472.1	364.3	407.4	778.7	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD15S4P1750R3-532AXSP06	297.2	456.6	351.7	393.1	-	296.1	452.9	349.3	391	-	372	24.3	3"	298	16.1	3"	446	34.2	3"
EAW-VD15S4P1750R3-625AXSP06	343	514.9	400.8	446.1	-	341.6	511	398.7	443.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4P1750R3-632AXSP06	325.9	494.3	382.8	427.1	-	324.3	490.1	380.6	424.5	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD15S4PK370C2-425AXSP06	225.6	348.9	267.9	300.5	-	225	346.7	266.7	298.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C2-432AXSP06	208.4	324.7	248.2	278.9	-	208	322.9	247.3	277.8	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C2-525AXSP06	253.4	387	298.7	333.9	-	252.8	384.5	297.7	332.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C2-532AXSP06	237.8	366.4	281.9	315.5	605.9	236.9	363.9	280.4	313.8	600.8	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C2-625AXSP06	272.9	412.3	320.1	356.8	668.8	272.1	409.1	318.4	354.4	662.9	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK370C2-632AXSP08	265.4	400.8	311.2	346.6	-	263.9	397.5	309.1	344.2	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370C4-425AXSP06	225.6	348.9	267.9	300.5	-	225	346.7	266.7	298.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C4-432AXSP06	208.4	324.7	248.2	278.9	-	208	322.9	247.3	277.8	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C4-525AXSP06	253.4	387	298.7	333.9	-	252.8	384.5	297.7	332.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C4-532AXSP06	237.8	366.4	281.9	315.5	605.9	236.9	363.9	280.4	313.8	600.8	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C4-625AXSP06	272.9	412.3	320.1	356.8	668.8	272.1	409.1	318.4	354.4	662.9	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK370C4-632AXSP08	265.4	400.8	311.2	346.6	-	263.9	397.5	309.1	344.2	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370C5-425AXSP06	225.6	348.9	267.9	300.5	-	225	346.7	266.7	298.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C5-432AXSP06	208.4	324.7	248.2	278.9	-	208	322.9	247.3	277.8	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C5-525AXSP06	253.4	387	298.7	333.9	-	252.8	384.5	297.7	332.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C5-532AXSP06	237.8	366.4	281.9	315.5	605.9	236.9	363.9	280.4	313.8	600.8	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C5-625AXSP06	272.9	412.3	320.1	356.8	668.8	272.1	409.1	318.4	354.4	662.9	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK370C5-632AXSP08	265.4	400.8	311.2	346.6	-	263.9	397.5	309.1	344.2	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370C8-425AXSP06	225.6	348.9	267.9	300.5	-	225	346.7	266.7	298.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C8-432AXSP06	208.4	324.7	248.2	278.9	-	208	322.9	247.3	277.8	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370C8-525AXSP06	253.4	387	298.7	333.9	-	252.8	384.5	297.7	332.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C8-532AXSP06	237.8	366.4	281.9	315.5	605.9	236.9	363.9	280.4	313.8	600.8	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370C8-625AXSP06	272.9	412.3	320.1	356.8	668.8	272.1	409.1	318.4	354.4	662.9	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK370C8-632AXSP08	265.4	400.8	311.2	346.6	-	263.9	397.5	309.1	344.2	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K2-425AXSP06	217.2	335.7	257.7	288.9	-	216.9	333.6	256.5	287.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K2-432AXSP06	201.1	313.1	239.4	268.8	-	200.7	310.8	238.4	267.7	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K2-525AXSP06	243.7	371.7	287.2	321	609.3	243.1	368.7	285.8	318.8	603.7	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370K2-532AXSP06	228.8	352.4	271.1	303.8	582.1	228.3	349.5	269.6	301.6	577.1	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370K2-625AXSP08	267.5	399.5	312	346.5	-	266.2	396.3	309.8	344.1	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K2-632AXSP08	254.9	385	298.9	333.1	-	253.7	381.8	296.8	330.7	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K4-425AXSP06	217.2	335.7	257.7	288.9	-	216.9	333.6	256.5	287.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K4-432AXSP06	201.1	313.1	239.4	268.8	-	200.7	310.8	238.4	267.7	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K4-525AXSP06	243.7	371.7	287.2	321	609.3	243.1	368.7	285.8	318.8	603.7	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370K4-532AXSP06	228.8	352.4	271.1	303.8	582.1	228.3	349.5	269.6	301.6	577.1	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370K4-625AXSP08	267.5	399.5	312	346.5	-	266.2	396.3	309.8	344.1	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K4-632AXSP08	254.9	385	298.9	333.1	-	253.7	381.8	296.8	330.7	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K5-425AXSP06	217.2	335.7	257.7	288.9	-	216.9	333.6	256.5	287.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K5-432AXSP06	201.1	313.1	239.4	268.8	-	200.7	310.8	238.4	267.7	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K5-525AXSP06	243.7	371.7	287.2	321	609.3	243.1	368.7	285.8	318.8	603.7	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370K5-532AXSP06	228.8	352.4	271.1	303.8	582.1	228.3	349.5	269.6	301.6	577.1	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370K5-625AXSP08	267.5	399.5	312	346.5	-	266.2	396.3	309.8	344.1	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K5-632AXSP08	254.9	385	298.9	333.1	-	253.7	381.8	296.8	330.7	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK370K8-425AXSP06	217.2	335.7	257.7	288.9	-	216.9	333.6	256.5	287.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K8-432AXSP06	201.1	313.1	239.4	268.8	-	200.7	310.8	238.4	267.7	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK370K8-525AXSP06	243.7	371.7	287.2	321	609.3	243.1	368.7	285.8	318.8	603.7	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK370																			

EAW-VD15S4PK400R3-625AXSP08	272	406.9	317.2	352.4	-	270.8	403.2	315.2	350.1	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK400R3-632AXSP08	259.4	391.4	304.2	339.1	-	258.3	388.3	302.1	336.3	-	338	26.7	3"	270	17.6	3"	406	37.4	3"
EAW-VD15S4PK550B3-425AXSP06	239.8	372.2	285.5	320.5	-	239.9	370.4	284.1	318.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550B3-432AXSP06	221.8	346.4	264.6	297.6	-	221.4	344.4	263.5	296.3	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550B3-525AXSP06	269.3	412.3	317.7	355.4	-	268.8	409.8	316.6	354.1	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550B3-532AXSP06	252.9	390.2	300	336.1	-	252.5	388.4	299.1	335	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550B3-625AXSP06	289.5	437.6	339.7	378.8	712.3	289.3	435.1	338.7	377.1	706.7	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550B3-632AXSP06	275.8	421.7	325.6	364	691.8	275.5	418.9	324.4	362	686.3	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C2-425AXSP06	251.6	390.9	299.2	336.2	-	251.2	388.8	298.2	334.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C2-432AXSP06	231.8	362.4	276.7	310.9	-	231.4	360.1	275.5	310	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C2-525AXSP06	284.3	436.3	336	376.2	-	284	433.2	334.7	374	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C2-532AXSP06	265.5	410.7	315.1	353.3	-	265.3	408.3	313.8	351.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C2-625AXSP06	307.7	466.6	361.7	403.5	-	307.2	463.4	360.2	401.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C2-632AXSP06	291.6	446	344.3	384.6	733.7	291.1	443.4	342.8	382.8	727.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C3-425AXSP06	251.6	390.9	299.2	336.2	-	251.2	388.8	298.2	334.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C3-432AXSP06	231.8	362.4	276.7	310.9	-	231.4	360.1	275.5	310	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C3-525AXSP06	284.3	436.3	336	376.2	-	284	433.2	334.7	374	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C3-532AXSP06	265.5	410.7	315.1	353.3	-	265.3	408.3	313.8	351.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C3-625AXSP06	307.7	466.6	361.7	403.5	-	307.2	463.4	360.2	401.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C3-632AXSP06	291.6	446	344.3	384.6	733.7	291.1	443.4	342.8	382.8	727.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C4-425AXSP06	251.6	390.9	299.2	336.2	-	251.2	388.8	298.2	334.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C4-432AXSP06	231.8	362.4	276.7	310.9	-	231.4	360.1	275.5	310	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C4-525AXSP06	284.3	436.3	336	376.2	-	284	433.2	334.7	374	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C4-532AXSP06	265.5	410.7	315.1	353.3	-	265.3	408.3	313.8	351.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C4-625AXSP06	307.7	466.6	361.7	403.5	-	307.2	463.4	360.2	401.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C4-632AXSP06	291.6	446	344.3	384.6	733.7	291.1	443.4	342.8	382.8	727.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C5-425AXSP06	251.6	390.9	299.2	336.2	-	251.2	388.8	298.2	334.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C5-432AXSP06	231.8	362.4	276.7	310.9	-	231.4	360.1	275.5	310	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C5-525AXSP06	284.3	436.3	336	376.2	-	284	433.2	334.7	374	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C5-532AXSP06	265.5	410.7	315.1	353.3	-	265.3	408.3	313.8	351.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C5-625AXSP06	307.7	466.6	361.7	403.5	-	307.2	463.4	360.2	401.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C5-632AXSP06	291.6	446	344.3	384.6	733.7	291.1	443.4	342.8	382.8	727.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C8-425AXSP06	251.6	390.9	299.2	336.2	-	251.2	388.8	298.2	334.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C8-432AXSP06	231.8	362.4	276.7	310.9	-	231.4	360.1	275.5	310	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C8-525AXSP06	284.3	436.3	336	376.2	-	284	433.2	334.7	374	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C8-532AXSP06	265.5	410.7	315.1	353.3	-	265.3	408.3	313.8	351.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C8-625AXSP06	307.7	466.6	361.7	403.5	-	307.2	463.4	360.2	401.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C8-632AXSP06	291.6	446	344.3	384.6	733.7	291.1	443.4	342.8	382.8	727.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C9-425AXSP06	251.6	390.9	299.2	336.2	-	251.2	388.8	298.2	334.9	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C9-432AXSP06	231.8	362.4	276.7	310.9	-	231.4	360.1	275.5	310	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550C9-525AXSP06	284.3	436.3	336	376.2	-	284	433.2	334.7	374	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C9-532AXSP06	265.5	410.7	315.1	353.3	-	265.3	408.3	313.8	351.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550C9-625AXSP06	307.7	466.6	361.7	403.5	-	307.2	463.4	360.2	401.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550C9-632AXSP06	291.6	446	344.3	384.6	733.7	291.1	443.4	342.8	382.8	727.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550K2-425AXSP06	240.7	373.7	286.6	321.8	-	240.8	371.8	285.2	320.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K2-432AXSP06	222.5	347.3	265.2	298.3	-	222.3	345.8	264.5	297	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K2-525AXSP06	270.9	414.8	320	358	-	270.6	412.6	318.8	356	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K2-532AXSP06	254.2	392.3	301.5	337.9	-	253.6	390	300.3	336.4	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K2-625AXSP06	292.5	442.1	343.2	382.7	719.8	291.9	439.1	341.7	380.5	713.3	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550K2-632AXSP06	277.8	424.2	327.5	366.1	696.9	277	421.8	326.6	364.5	691.2	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550K3-425AXSP06	240.7	373.7	286.6	321.8	-	240.8	371.8	285.2	320.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K3-432AXSP06	222.5	347.3	265.2	298.3	-	222.3	345.8	264.5	297	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K3-525AXSP06	270.9	414.8	320	358	-	270.6	412.6	318.8	356	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K3-532AXSP06	254.2	392.3	301.5	337.9	-	253.6	390	300.3	336.4	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K3-625AXSP06	292.5	442.1	343.2	382.7	719.8	291.9	439.1	341.7	380.5	713.3	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550K3-632AXSP06	277.8	424.2	327.5	366.1	696.9	277	421.8	326.6	364.5	691.2	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK550K4-425AXSP06	240.7	373.7	286.6	321.8	-	240.8	371.8	285.2	320.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K4-432AXSP06	222.5	347.3	265.2	298.3	-	222.3	345.8	264.5	297	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K4-525AXSP06	270.9	414.8	320	358	-	270.6	412.6	318.8	356	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K4-532AXSP06	254.2	392.3	301.5	337.9	-	253.6	390	300.3	336.4	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K5-425AXSP06	240.7	373.7	286.6	321.8	-	240.8	371.8	285.2	320.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K5-432AXSP06	222.5	347.3	265.2	298.3	-	222.3	345.8	264.5	297	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK550K5-525AXSP06	270.9	414.8	320	358	-	270.6	412.6	318.8	356	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K5-532AXSP06	254.2	392.3	301.5	337.9	-	253.6	390	300.3	336.4	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK550K6-425AXSP06	292.5	442.1	343.2	382.7	719.8	291.9	439.1	341.7	380.5	713.3	451	22.1	3"	361	14.5	3"			

EAW-VD15S4PK750C4-532AXSP06	281.7	436.5	334.6	376.2	-	281.5	434.7	333.9	374.6	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C4-625AXSP06	325.5	494.6	382.8	427.3	-	325.6	492.1	381.9	425.7	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C4-632AXSP06	309	473.9	362.2	408.7	-	308.6	471.2	364.2	406.9	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C5-425AXSP04	259.1	411.1	312.2	352.1	693.6	260.3	410.4	312.4	352.1	689.8	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750C5-432AXSP06	246.3	386	294.2	331.1	-	246.1	384.1	293.3	330.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750C5-525AXSP06	301.7	463.4	356.7	399.7	-	301.4	461	355.9	398	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C5-532AXSP06	281.7	436.5	334.6	376.2	-	281.5	434.7	333.9	374.6	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C5-625AXSP06	325.5	494.6	382.8	427.3	-	325.6	492.1	381.9	425.7	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C5-632AXSP06	309	473.9	365.2	408.7	-	308.6	471.2	364.2	406.9	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C8-425AXSP04	259.1	411.1	312.2	352.1	693.6	260.3	410.4	312.4	352.1	689.8	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750C8-432AXSP06	246.3	386	294.2	331.1	-	246.1	384.1	293.3	330.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750C8-525AXSP06	301.7	463.4	356.7	399.7	-	301.4	461	355.9	398	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C8-532AXSP06	281.7	436.5	334.6	376.2	-	281.5	434.7	333.9	374.6	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C8-625AXSP06	325.5	494.6	382.8	427.3	-	325.6	492.1	381.9	425.7	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C8-632AXSP06	309	473.9	365.2	408.7	-	308.6	471.2	364.2	406.9	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C9-425AXSP04	259.1	411.1	312.2	352.1	693.6	260.3	410.4	312.4	352.1	689.8	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750C9-432AXSP06	246.3	386	294.2	331.1	-	246.1	384.1	293.3	330.1	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750C9-525AXSP06	301.7	463.4	356.7	399.7	-	301.4	461	355.9	398	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C9-532AXSP06	281.7	436.5	334.6	376.2	-	281.5	434.7	333.9	374.6	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750C9-625AXSP06	325.5	494.6	382.8	427.3	-	325.6	492.1	381.9	425.7	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750C9-632AXSP06	309	473.9	365.2	408.7	-	308.6	471.2	364.2	406.9	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K2-425AXSP04	250.7	397.6	302.4	340.9	670.8	251.9	397	302.6	340.9	667.2	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750K2-432AXSP06	238.7	374	284.9	320.5	-	238.7	372.1	284.2	319.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750K2-525AXSP06	291.2	446.6	344.2	385.4	-	290.8	444.8	343.4	383.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K2-532AXSP06	272.6	422.3	323.7	363.1	-	272.5	420.1	323	362.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K2-625AXSP06	314.1	476.6	369.2	412	-	313.9	473.9	368.2	410.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K2-632AXSP06	298.3	456.9	352.4	394.3	752	298.3	454.3	351.4	392.5	746.6	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K3-425AXSP04	250.7	397.6	302.4	340.9	670.8	251.9	397	302.6	340.9	667.2	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750K3-432AXSP06	238.7	374	284.9	320.5	-	238.7	372.1	284.2	319.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750K3-525AXSP06	291.2	446.6	344.2	385.4	-	290.8	444.8	343.4	383.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K3-532AXSP06	272.6	422.3	323.7	363.1	-	272.5	420.1	323	362.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K3-625AXSP06	314.1	476.6	369.2	412	-	313.9	473.9	368.2	410.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K3-632AXSP06	298.3	456.9	352.4	394.3	752	298.3	454.3	351.4	392.5	746.6	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K4-425AXSP04	250.7	397.6	302.4	340.9	670.8	251.9	397	302.6	340.9	667.2	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750K4-432AXSP06	238.7	374	284.9	320.5	-	238.7	372.1	284.2	319.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750K4-525AXSP06	291.2	446.6	344.2	385.4	-	290.8	444.8	343.4	383.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K4-532AXSP06	272.6	422.3	323.7	363.1	-	272.5	420.1	323	362.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K4-625AXSP06	314.1	476.6	369.2	412	-	313.9	473.9	368.2	410.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K4-632AXSP06	298.3	456.9	352.4	394.3	752	298.3	454.3	351.4	392.5	746.6	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K5-425AXSP04	250.7	397.6	302.4	340.9	670.8	251.9	397	302.6	340.9	667.2	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750K5-432AXSP06	238.7	374	284.9	320.5	-	238.7	372.1	284.2	319.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750K5-525AXSP06	291.2	446.6	344.2	385.4	-	290.8	444.8	343.4	383.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K5-532AXSP06	272.6	422.3	323.7	363.1	-	272.5	420.1	323	362.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K5-625AXSP06	314.1	476.6	369.2	412	-	313.9	473.9	368.2	410.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K5-632AXSP06	298.3	456.9	352.4	394.3	752	298.3	454.3	351.4	392.5	746.6	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K8-425AXSP04	250.7	397.6	302.4	340.9	670.8	251.9	397	302.6	340.9	667.2	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750K8-432AXSP06	238.7	374	284.9	320.5	-	238.7	372.1	284.2	319.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750K8-525AXSP06	291.2	446.6	344.2	385.4	-	290.8	444.8	343.4	383.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K8-532AXSP06	272.6	422.3	323.7	363.1	-	272.5	420.1	323	362.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K8-625AXSP06	314.1	476.6	369.2	412	-	313.9	473.9	368.2	410.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K8-632AXSP06	298.3	456.9	352.4	394.3	752	298.3	454.3	351.4	392.5	746.6	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K9-425AXSP04	250.7	397.6	302.4	340.9	670.8	251.9	397	302.6	340.9	667.2	451	15.9	3"	361	10.5	3"	541	18.9	4"
EAW-VD15S4PK750K9-432AXSP06	238.7	374	284.9	320.5	-	238.7	372.1	284.2	319.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750K9-525AXSP06	291.2	446.6	344.2	385.4	-	290.8	444.8	343.4	383.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K9-532AXSP06	272.6	422.3	323.7	363.1	-	272.5	420.1	323	362.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750K9-625AXSP06	314.1	476.6	369.2	412	-	313.9	473.9	368.2	410.2	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750K9-632AXSP06	298.3	456.9	352.4	394.3	752	298.3	454.3	351.4	392.5	746.6	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750R3-425AXSP06	253.3	393.7	301.2	338.5	-	253.4	392.4	300.8	337.4	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750R3-432AXSP06	233.9	366.1	279.5	314.6	-	233.9	364.3	278.5	313.5	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD15S4PK750R3-525AXSP06	284.8	436.5	336.6	376.3	-	284.5	434.7	335.3	375.3	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750R3-532AXSP06	267.1	412.6	317	355.5	-	266.9	411	315.8	354	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD15S4PK750R3-625AXSP06	307	464.8	360.8	402	-	306.8	462.7	359.2	400.7	-	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4PK750R3-632AXSP06	291.9	446.6	344.3	385.1	734.6	291.4	444	343.2	383.8	729.4	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD15S4ZB370C2-425AXSP08	254.1	389.6	300	335.8	-	253	386.1	297.9	333.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB370C2-432AXSP08	235.2	362.8	278.4	312.5	-	234	359.8	276.6											

EAW-VD15S4ZB370K5-525AXSP08	268.9	406.1	315.3	351.4	-	267.2	402.5	312.9	348.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB370K5-532AXSP08	252.6	384.7	297.5	332.4	-	251	381.3	295.3	329.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB370K8-625AXSP08	289.6	432.4	337.7	375.4	696.6	287.9	427.9	335	372	688.1	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB370K5-632AXSP08	275.4	415.5	323.2	360	675.3	273.8	411.7	320.6	356.6	667.4	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB370K8-425AXSP08	244.9	374.4	289.2	323.4	-	243.6	371.2	286.7	320.6	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB370K8-432AXSP08	227.2	349.9	268.9	301.7	-	225.7	347.1	267.2	299.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB370K8-525AXSP08	268.9	406.1	315.3	351.4	-	267.2	402.5	312.9	348.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB370K8-532AXSP08	252.6	384.7	297.5	332.4	-	251	381.3	295.3	329.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB370K8-625AXSP08	289.6	432.4	337.7	375.4	696.6	287.9	427.9	335	372	688.1	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB370K8-632AXSP08	275.4	415.5	323.2	360	675.3	273.8	411.7	320.6	356.6	667.4	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400B3-425AXSP08	247.9	379.8	292.7	327.5	-	247	376.6	290.7	325.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400B3-432AXSP08	229.9	354.9	272.6	305.4	-	228.9	351.6	270.9	303.4	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400B3-525AXSP08	272.2	411.8	319.6	356.2	-	270.8	408.2	317.2	353.1	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400B3-532AXSP08	255.6	390.1	301.6	337	-	254.5	386.8	299	334	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400B3-625AXSP08	293.2	437.8	341.9	379.6	705.4	291.3	433.6	339	376.4	697.3	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400B3-632AXSP08	279.1	421.3	327.6	364.9	684.8	277.6	417.5	324.6	361.5	677	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400C3-425AXSP08	254.1	389.6	300	335.8	-	253	386.1	297.9	333.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400C3-432AXSP08	235.2	362.8	278.4	312.5	-	234	359.8	276.6	309.8	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400C3-525AXSP08	279.8	423.6	328.1	366.3	-	278	419.3	325.6	363	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400C3-532AXSP08	262.1	400.4	308.8	345.7	-	260.4	396.8	306.5	342.5	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400C3-625AXSP08	302.2	452.1	352.4	391.9	728.9	300.5	447.5	349.7	388.3	719.9	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400C3-632AXSP08	286.8	433.3	336.2	375.1	705.5	285.2	428.7	333.6	371.6	696.5	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400C9-425AXSP08	254.1	389.6	300	335.8	-	253	386.1	297.9	333.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400C9-432AXSP08	235.2	362.8	278.4	312.5	-	234	359.8	276.6	309.8	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400C9-525AXSP08	279.8	423.6	328.1	366.3	-	278	419.3	325.6	363	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400C9-532AXSP08	262.1	400.4	308.8	345.7	-	260.4	396.8	306.5	342.5	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400C9-625AXSP08	302.2	452.1	352.4	391.9	728.9	300.5	447.5	349.7	388.3	719.9	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400C9-632AXSP08	286.8	433.3	336.2	375.1	705.5	285.2	428.7	333.6	371.6	696.5	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400K3-425AXSP08	244.9	374.4	289.2	323.4	-	243.6	371.2	286.7	320.6	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400K3-432AXSP08	227.2	349.9	268.9	301.7	-	225.7	347.1	267.2	299.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400K3-525AXSP08	268.9	406.1	315.3	351.4	-	267.2	402.5	312.9	348.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400K3-532AXSP08	252.6	384.7	297.5	332.4	-	251	381.3	295.3	329.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400K3-625AXSP08	289.6	432.4	337.7	375.4	696.6	287.9	427.9	335	372	688.1	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400K3-632AXSP08	275.4	415.5	323.2	360	675.3	273.8	411.7	320.6	356.6	667.4	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400K9-425AXSP08	244.9	374.4	289.2	323.4	-	243.6	371.2	286.7	320.6	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400K9-432AXSP08	227.2	349.9	268.9	301.7	-	225.7	347.1	267.2	299.2	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400K9-525AXSP08	268.9	406.1	315.3	351.4	-	267.2	402.5	312.9	348.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400K9-532AXSP08	252.6	384.7	297.5	332.4	-	251	381.3	295.3	329.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400K9-625AXSP08	289.6	432.4	337.7	375.4	696.6	287.9	427.9	335	372	688.1	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400K9-632AXSP08	275.4	415.5	323.2	360	675.3	273.8	411.7	320.6	356.6	667.4	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400R3-425AXSP08	249.9	382.3	295	330.1	-	248.6	379.2	292.6	327.3	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400R3-432AXSP08	231.8	357.4	274.4	307.9	-	230.4	354.1	272.7	305.5	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB400R3-525AXSP08	274.2	414.3	321.5	358.4	-	272.5	410.8	319.2	355.8	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400R3-532AXSP08	257.6	392.7	303.4	339.1	-	256.1	389.4	301.3	336.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB400R3-625AXSP08	295.5	441.3	344.5	383.1	711.1	293.9	436.9	341.9	379.7	703.5	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB400R3-632AXSP08	281.1	424.4	329.5	367.1	690	279.3	420.1	327	364.3	682.2	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550B3-425AXSP06	266.4	412.8	316.6	355.5	-	265.8	409.8	314.9	353.3	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550B3-432AXSP08	252.1	389.8	299.2	335.7	-	250.8	387	297.2	333.3	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB550B3-525AXSP08	299.8	455	352.2	393	-	298.3	451	350.1	390.5	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550B3-532AXSP08	280.8	430.3	331.5	370.9	-	279.5	426.4	329.6	368.6	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550B3-625AXSP08	323.8	485.2	377.7	420.2	-	322.1	481.2	375.4	417.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550B3-632AXSP08	307.7	465.3	360.8	402.3	-	306	461.6	358.5	399.6	751.7	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550C2-425AXSP06	278.5	431.8	331.2	371.4	-	277.7	429.1	329.1	369.6	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550C2-432AXSP06	256.3	400.4	305.8	344.2	671.5	256	398.3	304.8	342.3	665.3	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550C2-525AXSP06	311.4	478	368.3	412.4	786.6	310.7	474.1	366.4	409.6	778.2	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB550C2-532AXSP08	293.9	450.6	347.2	388.7	-	292.4	446.9	344.9	385.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550C2-625AXSP08	342.1	513.4	399.6	444.8	-	339.9	509.1	396.8	441	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550C2-632AXSP08	323	489.9	379.5	423.9	-	321.6	485.8	376.8	420.3	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550C2-632AXSP06	278.5	431.8	331.2	371.4	-	277.7	429.1	329.1	369.6	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550C3-425AXSP06	256.3	400.4	305.8	344.2	671.5	256	398.3	304.8	342.3	665.3	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550C3-432AXSP06	311.4	478	368.3	412.4	786.6	310.7	474.1	366.4	409.6	778.2	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB550C3-525AXSP06	293.9	450.6	347.2	388.7	-	292.4	446.9	344.9	385.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550C3-625AXSP08	342.1	513.4	399.6	444.8	-	339.9	509.1	396.8	441	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550C3-632AXSP08	323	489.9	379.5	423.9	-	321.6	485.8	376.8	420.3	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB55																			

EAW-VD15S4ZB550K4-432AXSP08	252.5	391.2	299.8	336.3	-	251.7	387.8	298.3	333.9	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB550K4-525AXSP08	300.8	456.6	353.4	394.3	-	299.2	453	351.1	391.7	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K4-532AXSP08	281.7	431.1	332.6	372.2	-	280.4	427.7	330.1	369.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K4-625AXSP08	325.3	487.6	379.9	422.7	-	323.7	483.6	377.3	419.2	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K4-632AXSP08	308.7	467.5	362	404.2	-	306.9	463	359.6	400.8	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K5-425AXSP06	267.3	413.5	317.1	356	-	266.7	411.1	315.9	353.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550K5-432AXSP08	252.5	391.2	299.8	336.3	-	251.7	387.8	298.3	333.9	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB550K5-525AXSP08	300.8	456.6	353.4	394.3	-	299.2	453	351.1	391.7	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K5-532AXSP08	281.7	431.1	332.6	372.2	-	280.4	427.7	330.1	369.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K5-625AXSP08	325.3	487.6	379.9	422.7	-	323.7	483.6	377.3	419.2	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K5-632AXSP08	308.7	467.5	362	404.2	-	306.9	463	359.6	400.8	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K8-425AXSP06	267.3	413.5	317.1	356	-	266.7	411.1	315.9	353.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550K8-432AXSP08	252.5	391.2	299.8	336.3	-	251.7	387.8	298.3	333.9	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB550K8-525AXSP08	300.8	456.6	353.4	394.3	-	299.2	453	351.1	391.7	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K8-532AXSP08	281.7	431.1	332.6	372.2	-	280.4	427.7	330.1	369.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K8-625AXSP08	325.3	487.6	379.9	422.7	-	323.7	483.6	377.3	419.2	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K8-632AXSP08	308.7	467.5	362	404.2	-	306.9	463	359.6	400.8	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K9-425AXSP06	267.3	413.5	317.1	356	-	266.7	411.1	315.9	353.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550K9-432AXSP08	252.5	391.2	299.8	336.3	-	251.7	387.8	298.3	333.9	-	304	24.1	3"	244	15.9	3"	365	33.8	3"
EAW-VD15S4ZB550K9-525AXSP08	300.8	456.6	353.4	394.3	-	299.2	453	351.1	391.7	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K9-532AXSP08	281.7	431.1	332.6	372.2	-	280.4	427.7	330.1	369.2	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550K9-625AXSP08	325.3	487.6	379.9	422.7	-	323.7	483.6	377.3	419.2	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550K9-632AXSP08	308.7	467.5	362	404.2	-	306.9	463	359.6	400.8	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550R3-425AXSP06	274.4	425	326.2	365.7	-	273.8	422.8	324.5	363.7	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550R3-432AXSP06	253.2	396	302.1	339.9	662.5	252.6	393.5	301.3	338.3	657	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550R3-525AXSP08	308.9	469.4	363.5	405.7	-	307.3	465.8	360.8	402.6	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550R3-532AXSP08	289.2	443.1	341.6	382.3	-	287.9	439.8	339.6	379.4	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB550R3-625AXSP08	334.3	501.4	390.5	434.6	-	332.6	497.2	388.2	431.4	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550R3-632AXSP08	317	480.5	372.3	415.3	-	315.3	476	369.9	412.5	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB550C2-425AXSP06	297.9	463.7	354.6	398.8	-	297.7	460.9	353.7	396.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB550C2-432AXSP06	274.6	430.2	328.2	369.1	-	274.2	427.7	326.9	367.5	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C2-525AXSP06	333.7	512.2	394.9	441.9	845.5	333	509.5	392.9	439.6	838.7	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C2-532AXSP06	311.1	482.8	370.4	415.1	802.6	310.6	479.6	368.5	413.5	795.8	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C2-625AXSP08	365.1	550.5	427.8	476.4	-	363.9	546	424.9	473.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C2-632AXSP08	345.5	525.3	406.6	453.9	-	344	521.7	404.4	450.7	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C3-425AXSP06	297.9	463.7	354.6	398.8	-	297.7	460.9	353.7	396.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C3-432AXSP06	274.6	430.2	328.2	369.1	-	274.2	427.7	326.9	367.5	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C3-525AXSP06	333.7	512.2	394.9	441.9	845.5	333	509.5	392.9	439.6	838.7	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C3-532AXSP06	311.1	482.8	370.4	415.1	802.6	310.6	479.6	368.5	413.5	795.8	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C3-625AXSP08	365.1	550.5	427.8	476.4	-	363.9	546	424.9	473.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C3-632AXSP08	345.5	525.3	406.6	453.9	-	344	521.7	404.4	450.7	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C4-425AXSP06	297.9	463.7	354.6	398.8	-	297.7	460.9	353.7	396.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C4-432AXSP06	274.6	430.2	328.2	369.1	-	274.2	427.7	326.9	367.5	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C4-525AXSP06	333.7	512.2	394.9	441.9	845.5	333	509.5	392.9	439.6	838.7	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C4-532AXSP06	311.1	482.8	370.4	415.1	802.6	310.6	479.6	368.5	413.5	795.8	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C4-625AXSP08	365.1	550.5	427.8	476.4	-	363.9	546	424.9	473.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C4-632AXSP08	345.5	525.3	406.6	453.9	-	344	521.7	404.4	450.7	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C5-425AXSP06	297.9	463.7	354.6	398.8	-	297.7	460.9	353.7	396.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C5-432AXSP06	274.6	430.2	328.2	369.1	-	274.2	427.7	326.9	367.5	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C5-525AXSP06	333.7	512.2	394.9	441.9	845.5	333	509.5	392.9	439.6	838.7	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C5-532AXSP06	311.1	482.8	370.4	415.1	802.6	310.6	479.6	368.5	413.5	795.8	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C5-625AXSP08	365.1	550.5	427.8	476.4	-	363.9	546	424.9	473.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C5-632AXSP08	345.5	525.3	406.6	453.9	-	344	521.7	404.4	450.7	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C8-425AXSP06	297.9	463.7	354.6	398.8	-	297.7	460.9	353.7	396.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C8-432AXSP06	274.6	430.2	328.2	369.1	-	274.2	427.7	326.9	367.5	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C8-525AXSP06	333.7	512.2	394.9	441.9	845.5	333	509.5	392.9	439.6	838.7	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C8-532AXSP06	311.1	482.8	370.4	415.1	802.6	310.6	479.6	368.5	413.5	795.8	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C8-625AXSP08	365.1	550.5	427.8	476.4	-	363.9	546	424.9	473.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C8-632AXSP08	345.5	525.3	406.6	453.9	-	344	521.7	404.4	450.7	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C9-425AXSP06	297.9	463.7	354.6	398.8	-	297.7	460.9	353.7	396.9	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C9-432AXSP06	274.6	430.2	328.2	369.1	-	274.2	427.7	326.9	367.5	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750C9-525AXSP06	333.7	512.2	394.9	441.9	845.5	333	509.5	392.9	439.6	838.7	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C9-532AXSP06	311.1	482.8	370.4	415.1	802.6	310.6	479.6	368.5	413.5	795.8	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750C9-625AXSP08	365.1	550.5	427.8	476.4	-	363.9	546	424.9	473.1	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750C9-632AXSP08	345.5	525.3	406.6	453.9	-</														

EAW-VD15S4ZB750R3-425AXSP06	282.5	438.3	336	377.5	-	282.2	435.6	334.5	375.7	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750R3-432AXSP06	261.2	407.7	311.7	350.3	-	260.7	405.4	310.6	348.8	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD15S4ZB750R3-525AXSP06	315	482.9	372.5	416.6	795	314.1	479.6	370.5	414.2	788.4	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD15S4ZB750R3-532AXSP08	297.7	456.7	351.7	393.8	-	296.6	453.7	349.9	391.7	-	372	24.9	3"	298	16.4	3"	446	35	3"
EAW-VD15S4ZB750R3-625AXSP08	343.6	516.5	402	447.5	-	342.2	512.6	399.4	444.5	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZB750R3-632AXSP08	326.6	495.5	383.7	428.1	-	325.1	491.3	381.5	424.9	-	451	26.1	3"	361	17.2	3"	541	33.1	4"
EAW-VD15S4ZK017G7-425AXSP04	357	566	430.3	485.4	955.8	357.4	563.1	429	483.7	948.6	609	14.5	4"	487	12.5	3"	730	20.4	4"
EAW-VD15S4ZK017G7-432AXSP06	341.7	535.3	408	459.6	-	341	532	406.3	456.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK017G7-525AXSP06	423.1	651.7	501.3	560.9	-	421.7	646.5	498.1	558.1	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK017G7-532AXSP06	391.8	607.4	465.4	522.5	-	390.8	602.7	462.7	519.2	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK017G7-625AXSP06	461.8	702.8	543.2	606.7	-	459.8	696.9	540.2	602.4	-	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK017G7-632AXSP06	432.2	662.9	510.9	572.1	-	430.5	657.5	507.5	568.1	-	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK370C2-425AXSP06	261.7	402	309.5	346.7	664.6	260.4	398.2	307.5	343.9	656.2	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C2-432AXSP06	241.6	374.7	287.5	322.5	622.9	240.7	371.3	285.3	320	616.1	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C2-525AXSP08	294.2	443.2	344.4	383.2	-	291.9	438.1	341.3	379.7	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C2-532AXSP08	275.3	418.7	323.6	361.5	-	273.2	413.9	320.8	358.3	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C2-625AXSP08	317.7	472.7	369.4	410.1	-	315.1	467.3	366.1	405.9	749.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C2-632AXSP08	301.6	453.4	352.9	392.4	734.6	299.5	448	349.1	388.7	725.1	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C4-425AXSP06	261.7	402	309.5	346.7	664.6	260.4	398.2	307.5	343.9	656.2	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C4-432AXSP06	241.6	374.7	287.5	322.5	622.9	240.7	371.3	285.3	320	616.1	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C4-525AXSP08	294.2	443.2	344.4	383.2	-	291.9	438.1	341.3	379.7	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C4-532AXSP08	275.3	418.7	323.6	361.5	-	273.2	413.9	320.8	358.3	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C5-425AXSP08	317.7	472.7	369.4	410.1	-	315.1	467.3	366.1	405.9	749.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C5-432AXSP08	301.6	453.4	352.9	392.4	734.6	299.5	448	349.1	388.7	725.1	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C5-425AXSP06	261.7	402	309.5	346.7	664.6	260.4	398.2	307.5	343.9	656.2	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C5-432AXSP06	241.6	374.7	287.5	322.5	622.9	240.7	371.3	285.3	320	616.1	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C5-525AXSP08	294.2	443.2	344.4	383.2	-	291.9	438.1	341.3	379.7	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C5-532AXSP08	275.3	418.7	323.6	361.5	-	273.2	413.9	320.8	358.3	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C5-625AXSP08	317.7	472.7	369.4	410.1	-	315.1	467.3	366.1	405.9	749.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C5-632AXSP08	301.6	453.4	352.9	392.4	734.6	299.5	448	349.1	388.7	725.1	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C8-425AXSP06	261.7	402	309.5	346.7	664.6	260.4	398.2	307.5	343.9	656.2	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C8-432AXSP06	241.6	374.7	287.5	322.5	622.9	240.7	371.3	285.3	320	616.1	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370C8-525AXSP08	294.2	443.2	344.4	383.2	-	291.9	438.1	341.3	379.7	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C8-532AXSP08	275.3	418.7	323.6	361.5	-	273.2	413.9	320.8	358.3	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370C8-625AXSP08	317.7	472.7	369.4	410.1	-	315.1	467.3	366.1	405.9	749.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370C8-632AXSP08	301.6	453.4	352.9	392.4	734.6	299.5	448	349.1	388.7	725.1	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K2-425AXSP06	252	387.1	298.4	333.6	638.3	250.8	383.5	296	331.4	631.4	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370K2-432AXSP08	238.7	366.4	282.3	315.9	-	237.3	363	280.1	313.4	-	304	26.4	3"	244	17.4	3"	365	37	3"
EAW-VD15S4ZK370K2-525AXSP08	282.5	425.1	330.6	367.7	-	280.3	420.3	327.3	364.5	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K2-532AXSP08	265.3	402.9	311.8	348.1	-	263.4	398.4	309.2	344.6	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K2-625AXSP08	304.8	452.6	354	392.9	726.1	302.3	447	350.4	388.9	716.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K2-632AXSP08	289.7	434.9	338.4	376.7	704.2	287.7	429.9	335.4	372.8	694.6	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K4-425AXSP06	252	387.1	298.4	333.6	638.3	250.8	383.5	296	331.4	631.4	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370K4-432AXSP08	238.7	366.4	282.3	315.9	-	237.3	363	280.1	313.4	-	304	26.4	3"	244	17.4	3"	365	37	3"
EAW-VD15S4ZK370K4-525AXSP08	282.5	425.1	330.6	367.7	-	280.3	420.3	327.3	364.5	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K4-532AXSP08	265.3	402.9	311.8	348.1	-	263.4	398.4	309.2	344.6	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K4-625AXSP08	304.8	452.6	354	392.9	726.1	302.3	447	350.4	388.9	716.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K4-632AXSP08	289.7	434.9	338.4	376.7	704.2	287.7	429.9	335.4	372.8	694.6	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K5-425AXSP06	252	387.1	298.4	333.6	638.3	250.8	383.5	296	331.4	631.4	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370K5-432AXSP08	238.7	366.4	282.3	315.9	-	237.3	363	280.1	313.4	-	304	26.4	3"	244	17.4	3"	365	37	3"
EAW-VD15S4ZK370K5-525AXSP08	282.5	425.1	330.6	367.7	-	280.3	420.3	327.3	364.5	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K5-532AXSP08	265.3	402.9	311.8	348.1	-	263.4	398.4	309.2	344.6	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K5-625AXSP08	304.8	452.6	354	392.9	726.1	302.3	447	350.4	388.9	716.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K5-632AXSP08	289.7	434.9	338.4	376.7	704.2	287.7	429.9	335.4	372.8	694.6	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K8-425AXSP06	252	387.1	298.4	333.6	638.3	250.8	383.5	296	331.4	631.4	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK370K8-432AXSP08	238.7	366.4	282.3	315.9	-	237.3	363	280.1	313.4	-	304	26.4	3"	244	17.4	3"	365	37	3"
EAW-VD15S4ZK370K8-525AXSP08	282.5	425.1	330.6	367.7	-	280.3	420.3	327.3	364.5	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K8-532AXSP08	265.3	402.9	311.8	348.1	-	263.4	398.4	309.2	344.6	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK370K8-625AXSP08	304.8	452.6	354	392.9	726.1	302.3	447	350.4	388.9	716.5	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK370K8-632AXSP08	289.7	434.9	338.4	376.7	704.2	287.7	429.9	335.4	372.8	694.6	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK400B3-425AXSP06	255.6	392.9	302.2	338.5	648.1	254.4	389.3	300.4	335.8	641.1	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK400B3-432AXSP08	242	371.6	286.1	320.2	-	240.5	368.1	283.5	317.2	-	304	26.4	3"	244	17.4	3"	365	37	3"
EAW-VD15S4ZK400B3-525AXSP08	286.5	431.3	335.3	373.1	-	284.4	426.6	332.1	369.9	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD15S4ZK400B3-532AXSP08	269.1	408.4	316.3	353.2	-	267.2	404.4	313.7	349.7										

EAW-VD15S4ZK550B3-632AXSP08	324.8	489.3	380.2	423.1	-	322.6	484.2	376.7	419.7	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550C2-425AXSP06	293.9	453.3	348	390.5	-	292.8	449.3	346.1	387.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C2-432AXSP06	270.9	420.5	322.2	361.5	-	269.5	416.9	320	358.9	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C2-525AXSP06	329.2	501.5	387.8	432.7	821.8	327.3	496.7	384.7	429.7	811.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C2-532AXSP06	307.1	471.7	363.7	406.8	779.6	305.6	467.9	360.9	403.5	771.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C2-625AXSP06	354.6	535.1	416.4	463.3	867.5	353	530	413	459.5	857.5	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK550C2-632AXSP08	340.3	513.5	399	444.2	-	337.8	508.4	395.1	440.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550C3-425AXSP06	293.9	453.3	348	390.5	-	292.8	449.3	346.1	387.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C3-432AXSP06	270.9	420.5	322.2	361.5	-	269.5	416.9	320	358.9	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C3-525AXSP06	329.2	501.5	387.8	432.7	821.8	327.3	496.7	384.7	429.7	811.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C3-532AXSP06	307.1	471.7	363.7	406.8	779.6	305.6	467.9	360.9	403.5	771.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C3-625AXSP06	354.6	535.1	416.4	463.3	867.5	353	530	413	459.5	857.5	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK550C3-632AXSP08	340.3	513.5	399	444.2	-	337.8	508.4	395.1	440.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550C4-425AXSP06	293.9	453.3	348	390.5	-	292.8	449.3	346.1	387.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C4-432AXSP06	270.9	420.5	322.2	361.5	-	269.5	416.9	320	358.9	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C4-525AXSP06	329.2	501.5	387.8	432.7	821.8	327.3	496.7	384.7	429.7	811.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C4-532AXSP06	307.1	471.7	363.7	406.8	779.6	305.6	467.9	360.9	403.5	771.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C4-625AXSP06	354.6	535.1	416.4	463.3	867.5	353	530	413	459.5	857.5	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK550C4-632AXSP08	340.3	513.5	399	444.2	-	337.8	508.4	395.1	440.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550C5-425AXSP06	293.9	453.3	348	390.5	-	292.8	449.3	346.1	387.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C5-432AXSP06	270.9	420.5	322.2	361.5	-	269.5	416.9	320	358.9	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C5-525AXSP06	329.2	501.5	387.8	432.7	821.8	327.3	496.7	384.7	429.7	811.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C5-532AXSP06	307.1	471.7	363.7	406.8	779.6	305.6	467.9	360.9	403.5	771.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C5-625AXSP06	354.6	535.1	416.4	463.3	867.5	353	530	413	459.5	857.5	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK550C5-632AXSP08	340.3	513.5	399	444.2	-	337.8	508.4	395.1	440.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550C8-425AXSP06	293.9	453.3	348	390.5	-	292.8	449.3	346.1	387.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C8-432AXSP06	270.9	420.5	322.2	361.5	-	269.5	416.9	320	358.9	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C8-525AXSP06	329.2	501.5	387.8	432.7	821.8	327.3	496.7	384.7	429.7	811.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C8-532AXSP06	307.1	471.7	363.7	406.8	779.6	305.6	467.9	360.9	403.5	771.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C8-625AXSP06	354.6	535.1	416.4	463.3	867.5	353	530	413	459.5	857.5	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK550C8-632AXSP08	340.3	513.5	399	444.2	-	337.8	508.4	395.1	440.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550C9-425AXSP06	293.9	453.3	348	390.5	-	292.8	449.3	346.1	387.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C9-432AXSP06	270.9	420.5	322.2	361.5	-	269.5	416.9	320	358.9	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550C9-525AXSP06	329.2	501.5	387.8	432.7	821.8	327.3	496.7	384.7	429.7	811.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C9-532AXSP06	307.1	471.7	363.7	406.8	779.6	305.6	467.9	360.9	403.5	771.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550C9-625AXSP06	354.6	535.1	416.4	463.3	867.5	353	530	413	459.5	857.5	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK550C9-632AXSP08	340.3	513.5	399	444.2	-	337.8	508.4	395.1	440.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K2-425AXSP06	282.3	434.5	334.1	374.7	-	281.3	431.5	332.4	372.1	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K2-432AXSP06	261.1	405.1	310.4	348.6	675.4	260	402	308.5	346.4	668.8	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K2-525AXSP06	314.3	478.8	370.2	413.4	782.8	313.2	474.5	367.9	410.2	774.8	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K2-532AXSP06	294.1	452.4	348.8	389.9	745.9	293.3	448.4	346.3	387	738.2	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K2-625AXSP08	343.1	512	399.6	443.7	-	340.6	506.7	396.4	439.6	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K2-632AXSP08	325.4	490.3	380.9	424.5	-	323.2	485.1	377.9	420.5	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K3-425AXSP06	282.3	434.5	334.1	374.7	-	281.3	431.5	332.4	372.1	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K3-432AXSP06	261.1	405.1	310.4	348.6	675.4	260	402	308.5	346.4	668.8	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K3-525AXSP06	314.3	478.8	370.2	413.4	782.8	313.2	474.5	367.9	410.2	774.8	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K3-532AXSP06	294.1	452.4	348.8	389.9	745.9	293.3	448.4	346.3	387	738.2	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K3-625AXSP08	343.1	512	399.6	443.7	-	340.6	506.7	396.4	439.6	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K3-632AXSP08	325.4	490.3	380.9	424.5	-	323.2	485.1	377.9	420.5	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K4-425AXSP06	282.3	434.5	334.1	374.7	-	281.3	431.5	332.4	372.1	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K4-432AXSP06	261.1	405.1	310.4	348.6	675.4	260	402	308.5	346.4	668.8	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K4-525AXSP06	314.3	478.8	370.2	413.4	782.8	313.2	474.5	367.9	410.2	774.8	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K4-532AXSP06	294.1	452.4	348.8	389.9	745.9	293.3	448.4	346.3	387	738.2	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K4-625AXSP08	343.1	512	399.6	443.7	-	340.6	506.7	396.4	439.6	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K4-632AXSP08	325.4	490.3	380.9	424.5	-	323.2	485.1	377.9	420.5	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K5-425AXSP06	282.3	434.5	334.1	374.7	-	281.3	431.5	332.4	372.1	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K5-432AXSP06	261.1	405.1	310.4	348.6	675.4	260	402	308.5	346.4	668.8	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K5-525AXSP06	314.3	478.8	370.2	413.4	782.8	313.2	474.5	367.9	410.2	774.8	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K5-532AXSP06	294.1	452.4	348.8	389.9	745.9	293.3	448.4	346.3	387	738.2	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K5-625AXSP08	343.1	512	399.6	443.7	-	340.6	506.7	396.4	439.6	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K5-632AXSP08	325.4	490.3	380.9	424.5	-	323.2	485.1	377.9	420.5	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S4ZK550K8-425AXSP06	282.3	434.5	334.1	374.7	-	281.3	431.5	332.4	372.1	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K8-432AXSP06	261.1	405.1	310.4	348.6	675.4	260	402	308.5	346.4	668.8	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK550K8-525AXSP06	314.3	478.8	370.2	413.4	782.8	313.2	474.5	367.9	410.2	774.8	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK550K8-532																			

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S4ZK750C5-625AXSP06	381.6	576.2	447.7	498.4	936.4	380	571.7	444.7	495	926.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750C5-632AXSP06	360.2	549.9	425.1	475	901.5	358.6	545.3	422.7	471.6	892.7	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750C8-425AXSP06	315.6	488.5	374.6	420.1	-	314.8	484.7	373	417.5	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750C8-432AXSP06	290.6	453.1	346.7	389.5	-	290.3	450	344.3	386.7	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750C8-525AXSP06	353.6	540.2	416.8	466.1	-	352.2	535.9	414.7	462.9	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750C8-532AXSP06	330.2	508.9	391.4	438.2	841.8	329.1	504.8	388.9	435.3	833.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750C8-625AXSP06	381.6	576.2	447.7	498.4	936.4	380	571.7	444.7	495	926.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750C8-632AXSP06	360.2	549.9	425.1	475	901.5	358.6	545.3	422.7	471.6	892.7	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750C9-425AXSP06	315.6	488.5	374.6	420.1	-	314.8	484.7	373	417.5	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750C9-432AXSP06	290.6	453.1	346.7	389.5	-	290.3	450	344.3	386.7	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750C9-525AXSP06	353.6	540.2	416.8	466.1	-	352.2	535.9	414.7	462.9	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750C9-532AXSP06	330.2	508.9	391.4	438.2	841.8	329.1	504.8	388.9	435.3	833.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750C9-625AXSP06	381.6	576.2	447.7	498.4	936.4	380	571.7	444.7	495	926.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750C9-632AXSP06	360.2	549.9	425.1	475	901.5	358.6	545.3	422.7	471.6	892.7	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K2-425AXSP06	305.9	472.7	362.4	406.9	-	304.7	469.2	360.9	404.4	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K2-432AXSP06	282.3	439.3	336	377.9	-	281.5	436.4	334.4	375.3	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K2-525AXSP06	341.5	521.1	402.5	449.9	-	340.2	516.9	399.9	446.8	846.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K2-532AXSP06	319.3	491.3	378.3	423.4	813	318.3	487.5	376	420.6	805.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K2-625AXSP06	367.5	554.3	431	479.7	900.3	365.8	549.8	428	476.3	890.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K2-632AXSP06	347.5	530.6	409.9	457.9	867.9	346.5	526.2	407.7	454.7	859.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K3-425AXSP06	305.9	472.7	362.4	406.9	-	304.7	469.2	360.9	404.4	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K3-432AXSP06	282.3	439.3	336	377.9	-	281.5	436.4	334.4	375.3	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K3-525AXSP06	341.5	521.1	402.5	449.9	-	340.2	516.9	399.9	446.8	846.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K3-532AXSP06	319.3	491.3	378.3	423.4	813	318.3	487.5	376	420.6	805.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K3-625AXSP06	367.5	554.3	431	479.7	900.3	365.8	549.8	428	476.3	890.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K3-632AXSP06	347.5	530.6	409.9	457.9	867.9	346.5	526.2	407.7	454.7	859.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K4-425AXSP06	305.9	472.7	362.4	406.9	-	304.7	469.2	360.9	404.4	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K4-432AXSP06	282.3	439.3	336	377.9	-	281.5	436.4	334.4	375.3	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K4-525AXSP06	341.5	521.1	402.5	449.9	-	340.2	516.9	399.9	446.8	846.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K4-532AXSP06	319.3	491.3	378.3	423.4	813	318.3	487.5	376	420.6	805.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K4-625AXSP06	367.5	554.3	431	479.7	900.3	365.8	549.8	428	476.3	890.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K4-632AXSP06	347.5	530.6	409.9	457.9	867.9	346.5	526.2	407.7	454.7	859.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K5-425AXSP06	305.9	472.7	362.4	406.9	-	304.7	469.2	360.9	404.4	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K5-432AXSP06	282.3	439.3	336	377.9	-	281.5	436.4	334.4	375.3	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K5-525AXSP06	341.5	521.1	402.5	449.9	-	340.2	516.9	399.9	446.8	846.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K5-532AXSP06	319.3	491.3	378.3	423.4	813	318.3	487.5	376	420.6	805.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K5-625AXSP06	367.5	554.3	431	479.7	900.3	365.8	549.8	428	476.3	890.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K5-632AXSP06	347.5	530.6	409.9	457.9	867.9	346.5	526.2	407.7	454.7	859.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K8-425AXSP06	305.9	472.7	362.4	406.9	-	304.7	469.2	360.9	404.4	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K8-432AXSP06	282.3	439.3	336	377.9	-	281.5	436.4	334.4	375.3	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K8-525AXSP06	341.5	521.1	402.5	449.9	-	340.2	516.9	399.9	446.8	846.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K8-532AXSP06	319.3	491.3	378.3	423.4	813	318.3	487.5	376	420.6	805.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K8-625AXSP06	367.5	554.3	431	479.7	900.3	365.8	549.8	428	476.3	890.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K8-632AXSP06	347.5	530.6	409.9	457.9	867.9	346.5	526.2	407.7	454.7	859.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K9-425AXSP06	305.9	472.7	362.4	406.9	-	304.7	469.2	360.9	404.4	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K9-432AXSP06	282.3	439.3	336	377.9	-	281.5	436.4	334.4	375.3	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750K9-525AXSP06	341.5	521.1	402.5	449.9	-	340.2	516.9	399.9	446.8	846.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K9-532AXSP06	319.3	491.3	378.3	423.4	813	318.3	487.5	376	420.6	805.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750K9-625AXSP06	367.5	554.3	431	479.7	900.3	365.8	549.8	428	476.3	890.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750K9-632AXSP06	347.5	530.6	409.9	457.9	867.9	346.5	526.2	407.7	454.7	859.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750R3-425AXSP06	299.4	462.2	355.2	398	-	298.7	458.8	353.2	395.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750R3-432AXSP06	276.7	430.1	329.2	370.2	-	275.9	427.2	327.6	367.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD15S4ZK750R3-525AXSP06	333.8	508.8	393.3	439.5	834.1	332.4	504.8	391.3	436.5	826.3	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750R3-532AXSP06	312.4	481	370.1	414.7	794.4	311.4	477.3	367.8	412	786.9	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD15S4ZK750R3-625AXSP06	358.7	541.5	420.7	468.7	878	357	536.4	417.8	464.9	867.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD15S4ZK750R3-632AXSP08	345.1	521.6	404.6	451.1	-	343	516.6	401.8	447.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD15S5PB370C2-425AXSP04	262.8	412.3	314.6	353.9	690.6	263.1	410.5	314.4	352.9	686.2	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD15S5PB370C2-432AXSP06	248.8	387.8	296.5	333.4	-	248.6	385.4	295.2	331.2	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD15S5PB370C2-525AXSP06	302.4	461.1	356.1	397.7	-	301.7	458.1	354.7	396.1	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD15S5PB370C2-532AXSP06	283.7	436.4	335.8	376.1	-	283.1	434.2	334.6	374.1	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD15S5PB370C2-625AXSP06	324.9	489.3	380.7	423.8	-	324.1	486.4	378.9	421.8	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD15S5PB370C2-632AXSP06	310.2	471.6	365	407.3	-	309.2	468.3	362.9	404.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD15S5PB370C4-425AXSP04	262.8	412.3	314.6	353.9	690.6	263.1	410.5	314.4	352.9	686.2	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD15S5PB370C4-432AXSP06	248.8	387.8	296.5	333.4	-														

EAW-VD155SPB370K8-532AXSP06	273.5	420	323.6	362.3	-	272.9	417.1	321.9	360.3	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB370K8-625AXSP06	312.8	470.6	365.9	407.2	-	312.1	467.3	364.3	404.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB370K8-632AXSP06	298.2	452.9	350.8	391.3	740.9	297.6	449.6	348.7	389	734.7	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400B3-425AXSP04	255	400.2	305.7	343.8	670.7	255.8	399.2	305.5	343.4	666.5	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB400B3-432AXSP06	242.9	377.3	288.8	324.6	-	242.4	375.9	287.7	323.2	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD155SPB400B3-525AXSP06	292.7	445.8	344.6	384.7	-	292.2	443.2	343.1	382.9	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400B3-532AXSP06	276	424.1	326.1	365.2	-	275.5	421.3	325	363.8	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400B3-625AXSP06	313.6	471.2	366.9	408.3	-	313.2	468.9	365.5	406.8	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400B3-632AXSP06	300.3	456	352.7	394	745.3	299.6	453.2	351.5	392.1	739.8	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400C3-425AXSP04	262.8	412.3	314.6	353.9	690.6	263.1	410.5	314.4	352.9	686.2	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB400C3-432AXSP06	248.8	387.8	296.5	333.4	-	248.6	385.4	295.2	331.2	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD155SPB400C3-525AXSP06	302.4	461.1	356.1	397.7	-	301.7	458.1	354.7	396.1	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400C3-632AXSP06	283.7	436.4	335.8	376.1	-	283.1	434.2	334.6	374.1	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400C3-625AXSP06	324.9	489.3	380.7	423.8	-	324.1	486.4	378.9	421.8	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400C3-632AXSP06	310.2	471.6	365	407.3	-	309.2	468.3	362.9	404.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400C9-425AXSP04	262.8	412.3	314.6	353.9	690.6	263.1	410.5	314.4	352.9	686.2	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB400C9-432AXSP06	248.8	387.8	296.5	333.4	-	248.6	385.4	295.2	331.2	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD155SPB400C9-525AXSP06	302.4	461.1	356.1	397.7	-	301.7	458.1	354.7	396.1	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400C9-632AXSP06	283.7	436.4	335.8	376.1	-	283.1	434.2	334.6	374.1	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400C9-625AXSP06	324.9	489.3	380.7	423.8	-	324.1	486.4	378.9	421.8	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400C9-632AXSP06	310.2	471.6	365	407.3	-	309.2	468.3	362.9	404.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400K3-425AXSP04	252.6	396.9	302.8	341	663.8	253.2	395	302.4	339.8	659.3	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB400K3-432AXSP06	240.5	373.4	285.9	321.3	-	239.8	371	284.6	319.7	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD155SPB400K3-525AXSP06	290.7	442.6	342.1	382.5	-	289.8	440.1	340.7	380.3	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400K3-532AXSP06	273.5	420	323.6	362.3	-	272.9	417.1	321.9	360.3	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400K3-625AXSP06	312.8	470.6	365.9	407.2	-	312.1	467.3	364.3	404.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400K3-632AXSP06	298.2	452.9	350.8	391.3	740.9	297.6	449.6	348.7	389	734.7	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400K9-425AXSP04	252.6	396.9	302.8	341	663.8	253.2	395	302.4	339.8	659.3	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB400K9-432AXSP06	240.5	373.4	285.9	321.3	-	239.8	371	284.6	319.7	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD155SPB400K9-525AXSP06	290.7	442.6	342.1	382.5	-	289.8	440.1	340.7	380.3	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400K9-532AXSP06	273.5	420	323.6	362.3	-	272.9	417.1	321.9	360.3	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400K9-625AXSP06	312.8	470.6	365.9	407.2	-	312.1	467.3	364.3	404.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400K9-632AXSP06	298.2	452.9	350.8	391.3	740.9	297.6	449.6	348.7	389	734.7	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400R3-425AXSP04	257.3	403.2	307.9	346.8	675.8	257.6	402.1	307.7	345.9	671.6	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB400R3-432AXSP06	244.3	380.3	291	326.5	-	243.7	378.1	289.8	325.1	-	293	22.1	3"	234	18.7	2"	352	31.1	3"
EAW-VD155SPB400R3-525AXSP06	295.3	449.9	348.2	388.7	-	294.6	447.6	346.4	386.7	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400R3-632AXSP06	278	427.3	329	368.4	-	277.5	424.5	327.4	366.5	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB400R3-625AXSP06	318	477.9	372	414	-	317	474.8	370	411.8	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB400R3-632AXSP06	302.9	460.3	356.4	397.6	-	302.5	457.1	355	395.9	747.3	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50B3-425AXSP04	278.8	437.4	333.4	375.5	734.4	279.6	436.2	333.7	375	730.8	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50B3-432AXSP04	257.4	407.9	310.1	349.8	689.5	258.4	406.9	309.8	348.8	686.1	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50B3-525AXSP06	319.2	487.8	376.5	421.4	-	319.1	485.7	375.4	419.4	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB50B3-532AXSP06	300.3	463.3	355.7	398.7	-	300.2	460.9	355	397.2	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB50B3-625AXSP06	342.3	517	401.1	447.4	-	342.3	514.4	400.1	445.6	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50B3-632AXSP06	327.5	499	385.5	430.4	-	326.7	496.6	384.2	428.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C2-425AXSP04	293.1	460.7	351	395.6	-	293.9	459.9	351.1	394.8	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C2-432AXSP04	269.6	427.1	324.5	366.4	723.7	270.2	425.7	324.2	365.9	719.5	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C2-525AXSP04	326.8	508.6	389.9	437.7	846	327.7	507.3	389.6	436.5	841.2	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SPB50C2-532AXSP06	316.5	488.1	375.1	420.9	-	315.7	486	373.6	419	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB50C2-625AXSP06	365.3	553	428.9	478	-	364.7	550	427.1	475.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C2-632AXSP06	346.9	529.9	408.6	457.2	-	346.4	526.9	407.5	455.2	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C3-425AXSP04	293.1	460.7	351	395.6	-	293.9	459.9	351.1	394.8	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C3-432AXSP04	269.6	427.1	324.5	366.4	723.7	270.2	425.7	324.2	365.9	719.5	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C3-525AXSP04	326.8	508.6	389.9	437.7	846	327.7	507.3	389.6	436.5	841.2	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SPB50C3-532AXSP06	316.5	488.1	375.1	420.9	-	315.7	486	373.6	419	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB50C3-625AXSP06	365.3	553	428.9	478	-	364.7	550	427.1	475.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C3-632AXSP06	346.9	529.9	408.6	457.2	-	346.4	526.9	407.5	455.2	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C4-425AXSP04	293.1	460.7	351	395.6	-	293.9	459.9	351.1	394.8	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C4-432AXSP04	269.6	427.1	324.5	366.4	723.7	270.2	425.7	324.2	365.9	719.5	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C4-525AXSP04	326.8	508.6	389.9	437.7	846	327.7	507.3	389.6	436.5	841.2	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SPB50C4-532AXSP06	316.5	488.1	375.1	420.9	-	315.7	486	373.6	419	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SPB50C4-625AXSP06	365.3	553	428.9	478	-	364.7	550	427.1	475.9	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C4-632AXSP06	346.9	529.9	408.6	457.2	-	346.4	526.9	407.5	455.2	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SPB50C5-425AXSP04	293.1	460.7	351	395.6	-	293.9	459.9	351.1	394.8	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SPB50C5-432AXSP04	269.6	427.1	324.5	366.4	723.7	270.2	425.7	324.2	365.9	719.5	4								

EAW-VD155SP8550K5-525AXSP04	311.1	483.7	370.9	416.1	803.3	311.9	481.8	370.6	415.6	797.7	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8550K5-532AXSP06	302.4	466	358.2	401.6	-	301.6	463.4	356.8	399.9	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SP8550K5-625AXSP06	347.5	524.4	407.3	453.7	-	346.8	521.4	405.4	451.6	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550K5-632AXSP06	330.2	503.4	389.3	434.8	-	329.6	500.4	387.6	432.7	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550K8-425AXSP04	280	440.3	335.6	377.9	739.4	280.7	438.9	335.2	377.3	734.4	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8550K8-432AXSP04	258.4	409.6	311.3	351.2	692.6	259.2	408.3	310.9	350.7	687.6	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8550K8-525AXSP04	311.1	483.7	370.9	416.1	803.3	311.9	481.8	370.6	415.6	797.7	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8550K8-532AXSP06	302.4	466	358.2	401.6	-	301.6	463.4	356.8	399.9	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SP8550K8-625AXSP06	347.5	524.4	407.3	453.7	-	346.8	521.4	405.4	451.6	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550K8-632AXSP06	330.2	503.4	389.3	434.8	-	329.6	500.4	387.6	432.7	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550K9-425AXSP04	280	440.3	335.6	377.9	739.4	280.7	438.9	335.2	377.3	734.4	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8550K9-432AXSP04	258.4	409.6	311.3	351.2	692.6	259.2	408.3	310.9	350.7	687.6	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8550K9-525AXSP04	311.1	483.7	370.9	416.1	803.3	311.9	481.8	370.6	415.6	797.7	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8550K9-532AXSP06	302.4	466	358.2	401.6	-	301.6	463.4	356.8	399.9	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SP8550K9-625AXSP06	347.5	524.4	407.3	453.7	-	346.8	521.4	405.4	451.6	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550K9-632AXSP06	330.2	503.4	389.3	434.8	-	329.6	500.4	387.6	432.7	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550R3-425AXSP04	287.1	450.6	343.6	387.1	-	288	449.3	343.3	386.6	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8550R3-432AXSP04	264.7	419.1	318.8	359.8	709.5	265.4	418	318.6	358.8	705.9	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8550R3-525AXSP04	318.4	495.6	380.3	426.7	823.6	319.3	493.8	379.6	425.8	818.3	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8550R3-532AXSP06	309.5	477.5	366.7	411.3	-	308.9	475	365.4	409.7	-	372	23.1	3"	298	15.2	3"	446	32.4	3"
EAW-VD155SP8550R3-625AXSP06	355.7	537.8	417.5	465.1	-	355.1	535	415.8	463.2	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8550R3-632AXSP06	337.9	515.7	398.5	445.2	-	337.5	512.8	396.9	443.2	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750C2-425AXSP04	310.4	488.6	372	418.9	-	311.1	487.8	372.1	418.9	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C2-432AXSP04	285.7	452.8	344	388.3	-	287	452.2	343.9	387.7	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C2-462AXSP04	345.1	537.7	411.3	462.1	896	346.2	536.7	411.9	461.9	891.5	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C2-532AXSP04	322.7	507	386.6	435.3	851	323.8	505.9	387.2	435	847.3	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C2-625AXSP04	369.2	569.7	438.4	491.3	939.7	370.8	568.8	439	491.2	934.5	676	16.4	4"	541	10.8	4"	812	23	4"
EAW-VD155SP8750C2-632AXSP06	365.6	558.9	431.4	482.4	-	365.1	556.7	430.3	481	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750C3-425AXSP04	310.4	488.6	372	418.9	-	311.1	487.8	372.1	418.9	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C3-432AXSP04	285.7	452.8	344	388.3	-	287	452.2	343.9	387.7	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C3-462AXSP04	345.1	537.7	411.3	462.1	896	346.2	536.7	411.9	461.9	891.5	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C3-532AXSP04	322.7	507	386.6	435.3	851	323.8	505.9	387.2	435	847.3	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C3-625AXSP04	369.2	569.7	438.4	491.3	939.7	370.8	568.8	439	491.2	934.5	676	16.4	4"	541	10.8	4"	812	23	4"
EAW-VD155SP8750C3-632AXSP06	365.6	558.9	431.4	482.4	-	365.1	556.7	430.3	481	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750C4-425AXSP04	310.4	488.6	372	418.9	-	311.1	487.8	372.1	418.9	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C4-432AXSP04	285.7	452.8	344	388.3	-	287	452.2	343.9	387.7	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C4-462AXSP04	345.1	537.7	411.3	462.1	896	346.2	536.7	411.9	461.9	891.5	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C4-532AXSP04	322.7	507	386.6	435.3	851	323.8	505.9	387.2	435	847.3	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C4-625AXSP04	369.2	569.7	438.4	491.3	939.7	370.8	568.8	439	491.2	934.5	676	16.4	4"	541	10.8	4"	812	23	4"
EAW-VD155SP8750C4-632AXSP06	365.6	558.9	431.4	482.4	-	365.1	556.7	430.3	481	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750C8-425AXSP04	310.4	488.6	372	418.9	-	311.1	487.8	372.1	418.9	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C8-432AXSP04	285.7	452.8	344	388.3	-	287	452.2	343.9	387.7	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C8-525AXSP04	345.1	537.7	411.3	462.1	896	346.2	536.7	411.9	461.9	891.5	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C8-532AXSP04	322.7	507	386.6	435.3	851	323.8	505.9	387.2	435	847.3	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C8-625AXSP04	369.2	569.7	438.4	491.3	939.7	370.8	568.8	439	491.2	934.5	676	16.4	4"	541	10.8	4"	812	23	4"
EAW-VD155SP8750C8-632AXSP06	365.6	558.9	431.4	482.4	-	365.1	556.7	430.3	481	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750C9-425AXSP04	310.4	488.6	372	418.9	-	311.1	487.8	372.1	418.9	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C9-432AXSP04	285.7	452.8	344	388.3	-	287	452.2	343.9	387.7	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750C9-525AXSP04	345.1	537.7	411.3	462.1	896	346.2	536.7	411.9	461.9	891.5	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C9-532AXSP04	322.7	507	386.6	435.3	851	323.8	505.9	387.2	435	847.3	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750C9-625AXSP04	369.2	569.7	438.4	491.3	939.7	370.8	568.8	439	491.2	934.5	676	16.4	4"	541	10.8	4"	812	23	4"
EAW-VD155SP8750C9-632AXSP06	365.6	558.9	431.4	482.4	-	365.1	556.7	430.3	481	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750K2-425AXSP04	300.6	472.1	359.3	405.1	-	301.2	471.3	359.4	405	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750K2-432AXSP04	277	438.9	333.3	376	743.4	278	438.4	333.4	375.7	740.7	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750K2-525AXSP04	333.2	519.1	397.6	446.5	863.9	334.5	517.7	397.8	445.9	859	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750K2-532AXSP04	311.8	489.8	374.1	420.9	822.2	312.8	489.4	374.5	420.5	817.4	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750K2-625AXSP06	371.8	563	436.5	486.5	-	371.8	561	435.5	485.4	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750K2-632AXSP06	353.6	539.8	417.2	466.2	-	352.9	538	415.8	464.6	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750K3-425AXSP04	300.6	472.1	359.3	405.1	-	301.2	471.3	359.4	405	-	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750K3-432AXSP04	277	438.9	333.3	376	743.4	278	438.4	333.4	375.7	740.7	451	17.3	3"	361	11.4	3"	541	20.9	4"
EAW-VD155SP8750K3-525AXSP04	333.2	519.1	397.6	446.5	863.9	334.5	517.7	397.8	445.9	859	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750K3-532AXSP04	311.8	489.8	374.1	420.9	822.2	312.8	489.4	374.5	420.5	817.4	564	15.6	4"	451	12.7	3"	676	21.9	4"
EAW-VD155SP8750K3-625AXSP06	371.8	563	436.5	486.5	-	371.8	561	435.5	485.4	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750K3-632AXSP06	353.6	539.8	417.2	466.2	-	352.9	538	415.8	464.6	-	451	24.2	3"	361	16	3"	541	30.6	4"
EAW-VD155SP8750K4-42																			

EAW-VD155SP1370C2-432AXSP04	285.9	443.9	339.9	381.9	741.3	284.7	440.3	338.4	379.4	733.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C2-525AXSP04	344.6	525.2	406.5	453.4	859.8	343.5	520.6	403.6	450	850.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C2-532AXSP04	322.7	496.5	382.7	428.5	819.8	321.7	492	379.8	425.2	810.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C2-625AXSP04	370.1	557.9	434	483.3	902.9	368.6	552.9	431.2	479.6	892.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C2-632AXSP04	350.9	534.4	413.7	462.4	872.9	349.6	530.3	411.2	458.8	864	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C4-425AXSP04	309.6	477.4	367	411	-	308.4	473.3	364.5	408	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C4-432AXSP04	285.9	443.9	339.9	381.9	741.3	284.7	440.3	338.4	379.4	733.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C4-525AXSP04	344.6	525.2	406.5	453.4	859.8	343.5	520.6	403.6	450	850.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C4-532AXSP04	322.7	496.5	382.7	428.5	819.8	321.7	492	379.8	425.2	810.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C4-625AXSP04	370.1	557.9	434	483.3	902.9	368.6	552.9	431.2	479.6	892.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C4-632AXSP04	350.9	534.4	413.7	462.4	872.9	349.6	530.3	411.2	458.8	864	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C5-425AXSP04	309.6	477.4	367	411	-	308.4	473.3	364.5	408	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C5-432AXSP04	285.9	443.9	339.9	381.9	741.3	284.7	440.3	338.4	379.4	733.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C5-525AXSP04	344.6	525.2	406.5	453.4	859.8	343.5	520.6	403.6	450	850.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C5-532AXSP04	322.7	496.5	382.7	428.5	819.8	321.7	492	379.8	425.2	810.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C5-625AXSP04	370.1	557.9	434	483.3	902.9	368.6	552.9	431.2	479.6	892.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C5-632AXSP04	350.9	534.4	413.7	462.4	872.9	349.6	530.3	411.2	458.8	864	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C8-425AXSP04	309.6	477.4	367	411	-	308.4	473.3	364.5	408	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C8-432AXSP04	285.9	443.9	339.9	381.9	741.3	284.7	440.3	338.4	379.4	733.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370C8-525AXSP04	344.6	525.2	406.5	453.4	859.8	343.5	520.6	403.6	450	850.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C8-532AXSP04	322.7	496.5	382.7	428.5	819.8	321.7	492	379.8	425.2	810.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370C8-625AXSP04	370.1	557.9	434	483.3	902.9	368.6	552.9	431.2	479.6	892.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370C8-632AXSP04	350.9	534.4	413.7	462.4	872.9	349.6	530.3	411.2	458.8	864	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370K2-425AXSP04	298.5	458.8	353.2	395.3	-	297	455.7	350.8	392.5	751.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370K2-432AXSP04	275.8	428.2	328.4	368.7	714.1	275.2	425.5	326.4	366.4	707.2	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370K2-525AXSP04	330.9	503.5	390.2	435.6	823.7	329.7	499.1	387.3	432.3	814.4	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370K2-532AXSP04	310.4	477.6	368	411.9	786.7	309.6	473.4	365.4	408.8	778.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370K2-625AXSP04	354.8	534.2	415.9	463	863	352.8	529.4	412.7	458.9	853.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370K2-632AXSP04	337	513.2	397.2	443.8	836.5	335.7	508.5	394.2	440.3	826.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370K2-632AXSP04	298.5	458.8	353.2	395.3	-	297	455.7	350.8	392.5	751.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370K4-425AXSP04	275.8	428.2	328.4	368.7	714.1	275.2	425.5	326.4	366.4	707.2	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370K4-525AXSP04	330.9	503.5	390.2	435.6	823.7	329.7	499.1	387.3	432.3	814.4	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370K4-532AXSP04	310.4	477.6	368	411.9	786.7	309.6	473.4	365.4	408.8	778.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370K4-625AXSP04	354.8	534.2	415.9	463	863	352.8	529.4	412.7	458.9	853.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370K4-632AXSP04	337	513.2	397.2	443.8	836.5	335.7	508.5	394.2	440.3	826.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370K5-425AXSP04	298.5	458.8	353.2	395.3	-	297	455.7	350.8	392.5	751.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370K5-432AXSP04	275.8	428.2	328.4	368.7	714.1	275.2	425.5	326.4	366.4	707.2	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1370K5-525AXSP04	330.9	503.5	390.2	435.6	823.7	329.7	499.1	387.3	432.3	814.4	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370K5-532AXSP04	310.4	477.6	368	411.9	786.7	309.6	473.4	365.4	408.8	778.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1370K5-625AXSP04	354.8	534.2	415.9	463	863	352.8	529.4	412.7	458.9	853.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1370K5-632AXSP04	337	513.2	397.2	443.8	836.5	335.7	508.5	394.2	440.3	826.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400B3-425AXSP04	302.1	465.3	358	400.7	-	301.1	461.5	355.7	398.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400B3-432AXSP04	279.6	434.2	332.9	373.8	723.5	278.9	431	331	371.6	716.6	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400B3-525AXSP04	335.2	510.4	393.9	441.4	835.1	334.2	506.1	392.6	438.2	826.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400B3-532AXSP04	314.6	483.6	373	417.6	798	313.4	480.2	370.4	414.6	789	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400B3-625AXSP04	358.5	540.6	420.3	468	873.5	357.3	535.6	417.9	464.7	864.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400B3-632AXSP04	341.4	520.2	402.5	449.7	848.1	340.2	515.7	400.1	446.4	839.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400C3-425AXSP04	309.6	477.4	367	411	-	308.4	473.3	364.5	408	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400C3-432AXSP04	285.9	443.9	339.9	381.9	741.3	284.7	440.3	338.4	379.4	733.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400C3-525AXSP04	344.6	525.2	406.5	453.4	859.8	343.5	520.6	403.6	450	850.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400C3-532AXSP04	322.7	496.5	382.7	428.5	819.8	321.7	492	379.8	425.2	810.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400C3-625AXSP04	370.1	557.9	434	483.3	902.9	368.6	552.9	431.2	479.6	892.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400C3-632AXSP04	350.9	534.4	413.7	462.4	872.9	349.6	530.3	411.2	458.8	864	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400C9-425AXSP04	309.6	477.4	367	411	-	308.4	473.3	364.5	408	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400C9-432AXSP04	285.9	443.9	339.9	381.9	741.3	284.7	440.3	338.4	379.4	733.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400C9-525AXSP04	344.6	525.2	406.5	453.4	859.8	343.5	520.6	403.6	450	850.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400C9-532AXSP04	322.7	496.5	382.7	428.5	819.8	321.7	492	379.8	425.2	810.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400C9-625AXSP04	370.1	557.9	434	483.3	902.9	368.6	552.9	431.2	479.6	892.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400C9-632AXSP04	350.9	534.4	413.7	462.4	872.9	349.6	530.3	411.2	458.8	864	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1400K3-425AXSP04	298.5	458.8	353.2	395.3	-	297	455.7	350.8	392.5	751.9	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400K3-432AXSP04	275.8	428.2	328.4	368.7	714.1	275.2	425.5	326.4	366.4	707.2	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1400K3-525AXSP04	330.9	503.5	390.2	435.6	823.7	329.7	499.1	387.3	432.3	814.4	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1400K3-532AXSP04	310.4	477.6	368	411.9	786.7	309.6	473.4	365.4	408.8	778.7	564	19.8							

EAW-VD15SP1550C4-425AXSP04	346.6	536.7	411.5	461.5	-	345.7	532.6	409.8	458.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C4-432AXSP04	319.1	497.7	380.7	427.7	-	318.7	494.2	378.8	425.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C4-525AXSP04	388.7	594.1	458.3	512.4	-	387.2	589.3	455.9	509	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C4-532AXSP04	362.8	558.5	429.4	481.5	925.4	361.6	554.8	427.3	478.3	916.3	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C4-625AXSP04	419.2	634	491.8	548.3	1030.5	417.2	628.8	489.1	544.4	1019.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C4-632AXSP04	396	604.8	467.4	522.3	991.6	394.3	599.8	464.2	518.6	982.1	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C5-425AXSP04	346.6	536.7	411.5	461.5	-	345.7	532.6	409.8	458.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C5-432AXSP04	319.1	497.7	380.7	427.7	-	318.7	494.2	378.8	425.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C5-525AXSP04	388.7	594.1	458.3	512.4	-	387.2	589.3	455.9	509	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C5-532AXSP04	362.8	558.5	429.4	481.5	925.4	361.6	554.8	427.3	478.3	916.3	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C5-625AXSP04	419.2	634	491.8	548.3	1030.5	417.2	628.8	489.1	544.4	1019.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C5-632AXSP04	396	604.8	467.4	522.3	991.6	394.3	599.8	464.2	518.6	982.1	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C8-425AXSP04	346.6	536.7	411.5	461.5	-	345.7	532.6	409.8	458.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C8-432AXSP04	319.1	497.7	380.7	427.7	-	318.7	494.2	378.8	425.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C8-525AXSP04	388.7	594.1	458.3	512.4	-	387.2	589.3	455.9	509	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C8-532AXSP04	362.8	558.5	429.4	481.5	925.4	361.6	554.8	427.3	478.3	916.3	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C8-625AXSP04	419.2	634	491.8	548.3	1030.5	417.2	628.8	489.1	544.4	1019.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C8-632AXSP04	396	604.8	467.4	522.3	991.6	394.3	599.8	464.2	518.6	982.1	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C9-425AXSP04	346.6	536.7	411.5	461.5	-	345.7	532.6	409.8	458.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C9-432AXSP04	319.1	497.7	380.7	427.7	-	318.7	494.2	378.8	425.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550C9-525AXSP04	388.7	594.1	458.3	512.4	-	387.2	589.3	455.9	509	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C9-532AXSP04	362.8	558.5	429.4	481.5	925.4	361.6	554.8	427.3	478.3	916.3	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550C9-625AXSP04	419.2	634	491.8	548.3	1030.5	417.2	628.8	489.1	544.4	1019.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550C9-632AXSP04	396	604.8	467.4	522.3	991.6	394.3	599.8	464.2	518.6	982.1	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K2-425AXSP04	332.6	513.8	394.6	442.3	-	331.9	510.2	392.5	439.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K2-432AXSP04	307.2	478.1	365.6	411.3	-	306.4	475	363.9	408.5	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K2-525AXSP04	370.9	565.8	437.1	488.5	929.1	369.5	561.4	435	485.3	919.5	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K2-532AXSP04	347.1	534.9	411.3	461	883.9	346.1	530.8	409.4	458.1	875.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K2-625AXSP04	398.5	601.9	468.1	520.9	977.5	396.9	597.3	465.1	517.5	966.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K2-632AXSP04	377.4	576.3	445.9	498	943.8	376.4	571.6	442.9	494.6	933.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K3-425AXSP04	332.6	513.8	394.6	442.3	-	331.9	510.2	392.5	439.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K3-432AXSP04	307.2	478.1	365.6	411.3	-	306.4	475	363.9	408.5	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K3-525AXSP04	370.9	565.8	437.1	488.5	929.1	369.5	561.4	435	485.3	919.5	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K3-532AXSP04	347.1	534.9	411.3	461	883.9	346.1	530.8	409.4	458.1	875.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K3-625AXSP04	398.5	601.9	468.1	520.9	977.5	396.9	597.3	465.1	517.5	966.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K3-632AXSP04	377.4	576.3	445.9	498	943.8	376.4	571.6	442.9	494.6	933.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K4-425AXSP04	332.6	513.8	394.6	442.3	-	331.9	510.2	392.5	439.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K4-432AXSP04	307.2	478.1	365.6	411.3	-	306.4	475	363.9	408.5	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K4-525AXSP04	370.9	565.8	437.1	488.5	929.1	369.5	561.4	435	485.3	919.5	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K4-625AXSP04	347.1	534.9	411.3	461	883.9	346.1	530.8	409.4	458.1	875.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K4-632AXSP04	398.5	601.9	468.1	520.9	977.5	396.9	597.3	465.1	517.5	966.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K5-425AXSP04	332.6	513.8	394.6	442.3	-	331.9	510.2	392.5	439.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K5-432AXSP04	307.2	478.1	365.6	411.3	-	306.4	475	363.9	408.5	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K5-525AXSP04	370.9	565.8	437.1	488.5	929.1	369.5	561.4	435	485.3	919.5	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K5-532AXSP04	347.1	534.9	411.3	461	883.9	346.1	530.8	409.4	458.1	875.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K5-625AXSP04	398.5	601.9	468.1	520.9	977.5	396.9	597.3	465.1	517.5	966.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K5-632AXSP04	377.4	576.3	445.9	498	943.8	376.4	571.6	442.9	494.6	933.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K8-425AXSP04	332.6	513.8	394.6	442.3	-	331.9	510.2	392.5	439.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K8-432AXSP04	307.2	478.1	365.6	411.3	-	306.4	475	363.9	408.5	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K8-525AXSP04	370.9	565.8	437.1	488.5	929.1	369.5	561.4	435	485.3	919.5	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K8-625AXSP04	347.1	534.9	411.3	461	883.9	346.1	530.8	409.4	458.1	875.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K8-632AXSP04	398.5	601.9	468.1	520.9	977.5	396.9	597.3	465.1	517.5	966.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550K9-425AXSP04	332.6	513.8	394.6	442.3	-	331.9	510.2	392.5	439.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K9-432AXSP04	307.2	478.1	365.6	411.3	-	306.4	475	363.9	408.5	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550K9-525AXSP04	370.9	565.8	437.1	488.5	929.1	369.5	561.4	435	485.3	919.5	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K9-625AXSP04	347.1	534.9	411.3	461	883.9	346.1	530.8	409.4	458.1	875.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550K9-632AXSP04	398.5	601.9	468.1	520.9	977.5	396.9	597.3	465.1	517.5	966.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550R3-425AXSP04	341.3	528.1	405.1	454.3	-	340.7	524.5	403.1	451.9	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550R3-432AXSP04	315.7	491.1	375.9	422.2	-	314.9	488.1	374.3	420.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15SP1550R3-525AXSP04	381.3	582.4	449.5	502.5	-	380.1	578	446.8	499.5	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550R3-532AXSP04	356.8	549.7	422.9	473.4	910.2	355.3	545.7	420.5	470.6	901	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15SP1550R3-625AXSP04	409.4	618.9	480.9	535.4	1005.5	408	614.5	478.2	532.3	996.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1550R3-632AXSP04	387.9	592.9	458.5	511.5	971.7	386.5	588.4	455.6	508.2	961.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15SP1750C2-425AXSP04	371.3	575.1	441.2	495.3	-	370.3	571.7	439.3	492.2	-	451	21.							

EAW-VD155SP1750C9-632AXSP04	423.7	647.9	500.4	558.8	1065.4	422.7	643.6	497.8	555.7	1055.4	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K2-425AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K2-432AXSP04	331.5	517.3	395	444	-	331	513.6	393.6	442.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K2-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K2-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K2-625AXSP04	431.7	652.8	506.6	565	1062.8	430.7	648.7	504.2	561.4	1053.8	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K2-632AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K3-425AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K3-432AXSP04	331.5	517.3	395	444	-	331	513.6	393.6	442.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K3-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K3-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K3-625AXSP04	431.7	652.8	506.6	565	1062.8	430.7	648.7	504.2	561.4	1053.8	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K3-632AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K4-425AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K4-432AXSP04	331.5	517.3	395	444	-	331	513.6	393.6	442.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K4-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K4-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K5-425AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K5-432AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K5-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K5-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K6-425AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K6-432AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K6-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K6-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K8-425AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K8-432AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K8-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K8-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K8-625AXSP04	431.7	652.8	506.6	565	1062.8	430.7	648.7	504.2	561.4	1053.8	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K8-632AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K9-425AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K9-432AXSP04	331.5	517.3	395	444	-	331	513.6	393.6	442.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K9-525AXSP04	401.5	613.5	473.5	529.6	-	400.5	609.4	471.7	526.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K9-532AXSP04	375.2	578.6	445	498.5	-	374.6	574.8	442.8	496	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750K5-625AXSP04	431.7	652.8	506.6	565	1062.8	430.7	648.7	504.2	561.4	1053.8	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K5-632AXSP04	408.8	625.2	482.7	539.6	1025.9	407.7	620.8	480	536.5	1017.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750K8-625AXSP04	359	556	426.4	478.5	-	358	552.7	424.5	476.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750K8-632AXSP04	331.5	517.3	395	444	-	331	513.6	393.6	442.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750R3-425AXSP04	352	544.5	417.9	468.8	-	351	541.2	416.1	465.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750R3-432AXSP04	324.9	506.4	387	435	-	324.4	503.6	385.7	433.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD155SP1750R3-525AXSP04	392.3	599.8	463.2	518	-	391.3	595.8	460.8	514.5	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750R3-532AXSP04	367.2	566.5	435.3	488.3	939	366.5	562.8	433.2	485	931.2	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD155SP1750R3-625AXSP04	421.3	637.3	494.3	551.1	1035.9	420.2	632.5	491.8	548.3	1027	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SP1750R3-632AXSP04	399.5	610.5	472.3	527.1	1002.5	398.4	606.2	469.6	524	992.8	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD155SPK370C2-425AXSP04	280	436.1	334.3	375	728.7	280.3	434.1	332.8	373.8	722.9	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C2-432AXSP04	258.5	406.5	309.7	348.7	682.1	258.6	404.3	309.1	347.2	676.8	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C2-525AXSP04	311.5	479.8	369.5	413.8	790.8	311.4	476.8	368.3	411.8	784.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK370C2-532AXSP06	301.7	461.3	355.8	398.1	-	300	458.2	353.9	395.3	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK370C2-625AXSP06	346.2	519.1	404.4	450	-	344.7	515.1	401.7	446.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK370C2-632AXSP06	329.4	499	386.9	431.4	-	328	495	384.2	428.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK370C4-425AXSP04	280	436.1	334.3	375	728.7	280.3	434.1	332.8	373.8	722.9	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C4-432AXSP04	258.5	406.5	309.7	348.7	682.1	258.6	404.3	309.1	347.2	676.8	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C4-525AXSP04	311.5	479.8	369.5	413.8	790.8	311.4	476.8	368.3	411.8	784.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK370C4-532AXSP06	301.7	461.3	355.8	398.1	-	300	458.2	353.9	395.3	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK370C4-625AXSP06	346.2	519.1	404.4	450	-	344.7	515.1	401.7	446.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK370C4-632AXSP06	329.4	499	386.9	431.4	-	328	495	384.2	428.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK370C5-425AXSP04	280	436.1	334.3	375	728.7	280.3	434.1	332.8	373.8	722.9	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C5-432AXSP04	258.5	406.5	309.7	348.7	682.1	258.6	404.3	309.1	347.2	676.8	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C5-525AXSP04	311.5	479.8	369.5	413.8	790.8	311.4	476.8	368.3	411.8	784.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK370C5-532AXSP06	301.7	461.3	355.8	398.1	-	300	458.2	353.9	395.3	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK370C5-625AXSP06	346.2	519.1	404.4	450	-	344.7	515.1	401.7	446.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK370C5-632AXSP06	329.4	499	386.9	431.4	-	328	495	384.2	428.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK370C8-425AXSP04	280	436.1	334.3	375	728.7	280.3	434.1	332.8	373.8	722.9	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK370C8-432AXSP04	258.5	406.5	309.7	348.7	682.1	258.6													

EAW-VD155SPK400C3-625AXSP06	346.2	519.1	404.4	450	-	344.7	515.1	401.7	446.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400C3-632AXSP06	329.4	499	386.9	431.4	-	328	495	384.2	428.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400C9-425AXSP04	280	436.1	334.3	375	728.7	280.3	434.1	332.8	373.8	722.9	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400C9-432AXSP04	258.5	406.5	309.7	348.7	682.1	258.6	404.3	309.1	347.2	676.8	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400C9-525AXSP04	311.5	479.8	369.5	413.8	790.8	311.4	476.8	368.3	411.8	784.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK400C9-532AXSP06	301.7	461.3	355.8	398.1	-	300	458.2	353.9	395.3	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK400C9-625AXSP06	346.2	519.1	404.4	450	-	344.7	515.1	401.7	446.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400C9-632AXSP06	329.4	499	386.9	431.4	-	328	495	384.2	428.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400K3-425AXSP04	269.6	419.6	321.6	361.1	699.2	269.7	417.6	320.6	359.3	693.5	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400K3-432AXSP04	249.4	391.4	299.2	336.6	656.8	249.4	389.8	298.1	335.2	651.6	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400K3-525AXSP06	308.8	468.3	362.7	404.6	-	307.5	464.6	360.8	401.9	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK400K3-532AXSP06	290.2	443.7	342.6	383.2	-	289	440.6	340.2	380.5	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK400K3-625AXSP06	332.6	497.6	388	431.5	-	331	493.6	385.3	428	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400K3-632AXSP06	316.9	478.8	371.5	414.2	-	315.4	475.4	369.4	411.2	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400K9-425AXSP04	269.6	419.6	321.6	361.1	699.2	269.7	417.6	320.6	359.3	693.5	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400K9-432AXSP04	249.4	391.4	299.2	336.6	656.8	249.4	389.8	298.1	335.2	651.6	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400K9-525AXSP06	308.8	468.3	362.7	404.6	-	307.5	464.6	360.8	401.9	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK400K9-532AXSP06	290.2	443.7	342.6	383.2	-	289	440.6	340.2	380.5	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK400K9-625AXSP06	332.6	497.6	388	431.5	-	331	493.6	385.3	428	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400K9-632AXSP06	316.9	478.8	371.5	414.2	-	315.4	475.4	369.4	411.2	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400R3-425AXSP04	274.6	427.9	327.7	367.5	713.4	274.4	425.4	326.4	366.4	707.9	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400R3-432AXSP04	253.7	399.3	304.4	342.6	669.4	253.8	397.1	303.4	341.3	664.4	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK400R3-525AXSP06	304.4	469.2	361.1	404.3	772.9	304.4	466.4	360	403	766.1	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK400R3-532AXSP06	295.6	452.3	348.5	389.9	-	294.1	448.7	346.8	387.3	-	372	25.2	3"	298	16.6	3"	446	35.4	3"
EAW-VD155SPK400R3-625AXSP06	338.2	506.1	394.5	438.9	-	336.7	502.3	391.9	436	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK400R3-632AXSP06	322.4	487.4	378.1	421.5	-	321	483.5	376.1	418.7	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK500B3-425AXSP04	298.7	465.9	356.2	400	-	298.9	463.7	355.2	398.7	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK500B3-432AXSP04	275.6	433.8	330.1	372	729.9	275.7	432	329.4	371.1	725.2	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK500B3-525AXSP06	331	511.2	392.9	440.4	844.9	331.4	508.7	392.2	438.8	838.5	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK500B3-532AXSP06	310.8	484.1	370.6	416.1	806.1	310.9	481.9	370.2	414.8	800.9	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK500B3-625AXSP06	366.9	551.8	429.3	477.9	-	366.1	547.9	427.3	475.1	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK500B3-632AXSP06	350	531.4	411.2	458.9	-	349	527.8	409.6	456.3	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK550C2-425AXSP04	313.4	489.4	373.3	420.3	-	313.4	486.8	372.7	418.7	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C2-432AXSP04	288.2	453.8	345.2	388.7	-	288.4	451.8	344.3	387.5	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C2-525AXSP04	349.8	540.8	415.5	465.3	895.3	350	537.8	414.5	464.1	887.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C2-532AXSP04	326.7	509.4	389.9	438	849.7	326.5	506.5	388.3	436.2	843.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C2-625AXSP04	376.5	575.8	445.2	497.6	943.7	376.5	572.7	444.1	495.5	936.3	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550C2-632AXSP04	355.5	549.9	422.7	474.4	909	355.6	547.5	421.5	472.3	901.2	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550C3-425AXSP04	313.4	489.4	373.3	420.3	-	313.4	486.8	372.7	418.7	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C3-432AXSP04	288.2	453.8	345.2	388.7	-	288.4	451.8	344.3	387.5	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C3-525AXSP04	349.8	540.8	415.5	465.3	895.3	350	537.8	414.5	464.1	887.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C3-625AXSP04	326.7	509.4	389.9	438	849.7	326.5	506.5	388.3	436.2	843.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C3-632AXSP04	355.5	549.9	422.7	474.4	909	355.6	547.5	421.5	472.3	901.2	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550C4-425AXSP04	313.4	489.4	373.3	420.3	-	313.4	486.8	372.7	418.7	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C4-432AXSP04	288.2	453.8	345.2	388.7	-	288.4	451.8	344.3	387.5	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C4-525AXSP04	349.8	540.8	415.5	465.3	895.3	350	537.8	414.5	464.1	887.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C4-532AXSP04	326.7	509.4	389.9	438	849.7	326.5	506.5	388.3	436.2	843.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C4-625AXSP04	376.5	575.8	445.2	497.6	943.7	376.5	572.7	444.1	495.5	936.3	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550C4-632AXSP04	355.5	549.9	422.7	474.4	909	355.6	547.5	421.5	472.3	901.2	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550C5-425AXSP04	313.4	489.4	373.3	420.3	-	313.4	486.8	372.7	418.7	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C5-432AXSP04	288.2	453.8	345.2	388.7	-	288.4	451.8	344.3	387.5	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C5-525AXSP04	349.8	540.8	415.5	465.3	895.3	350	537.8	414.5	464.1	887.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C5-625AXSP04	326.7	509.4	389.9	438	849.7	326.5	506.5	388.3	436.2	843.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C5-632AXSP04	355.5	549.9	422.7	474.4	909	355.6	547.5	421.5	472.3	901.2	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550C6-425AXSP04	313.4	489.4	373.3	420.3	-	313.4	486.8	372.7	418.7	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C6-432AXSP04	288.2	453.8	345.2	388.7	-	288.4	451.8	344.3	387.5	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550C6-525AXSP04	349.8	540.8	415.5	465.3	895.3	350	537.8	414.5	464.1	887.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550C6-625AXSP04	326.7	509.4	389.9	438	849.7	326.5	506.5	388.3	436.2	843.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550K2-525AXSP04	333.3	514.2	395.7	443.6	850.1	333.6	511.5	394.9	441.8	843.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550K2-532AXSP04	311.8	486.6	372.5	418.2	810.4	312.2	483.9	371.7	416.5	803.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550K2-625AXSP06	357	545.7	422	471.4	892.3	356.9	542.8	420.9	470	885.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550K2-632AXSP06	352.5	534.6	414.2	462.2	-	350.9	530.8	411.8	459.5	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK550K3-425AXSP04	299.8	467.9	357.6	401.6	-	299.9	465.5	356.5	400.1	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550K3-432AXSP04	276.5	434.9	331.5	372.9	731.9	276.8	433	330.7	371.9	727	451	18.7	3						

EAW-VD155SPK550K9-532AXSP04	311.8	486.6	372.5	418.2	810.4	312.2	483.9	371.7	416.5	803.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550K9-625AXSP04	357	545.7	422	471.4	892.3	356.9	542.8	420.9	470	885.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550K9-632AXSP06	352.5	534.6	414.2	462.2	-	350.9	530.8	411.8	459.5	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK550R3-425AXSP04	307.5	479.7	366.3	412.2	-	307.2	477.5	365.9	410.9	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550R3-432AXSP04	283.4	445.7	339.2	382.6	750.9	283.7	443.9	338.6	381.7	746.2	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK550R3-525AXSP04	341.7	527.6	405.8	454.3	873	342.1	525.1	404.5	453.4	866.3	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550R3-532AXSP04	319.6	498.7	382	429	831.3	320.3	496.3	380.8	427.6	825.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK550R3-625AXSP04	366.3	560.4	433.1	483.9	916.8	366.4	557.6	431.5	482.1	910	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK550R3-632AXSP06	360.8	548.4	424.6	474	-	359.8	544.8	422.4	471.4	-	451	26.3	3"	361	17.4	3"	541	33.6	4"
EAW-VD155SPK750C2-425AXSP04	332.8	520.9	397.6	447.3	-	332.9	519.1	397	446.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C2-432AXSP04	306.5	483.4	367.3	413.9	-	306.9	481	367	413.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C2-525AXSP04	371.6	574.3	441	494.2	-	371.9	572.1	440	493	-	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C2-532AXSP04	347.1	541.4	413.9	465.5	905.2	347.6	539.2	413	464.3	899.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C2-625AXSP04	398.2	610.2	471.1	526.8	1002.6	399	608.1	470.8	525.6	995.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C2-632AXSP04	377.1	584.1	448.7	503.3	967.1	377.9	581.7	448.3	501.9	960.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C3-425AXSP04	332.8	520.9	397.6	447.3	-	332.9	519.1	397	446.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C3-432AXSP04	306.5	483.4	367.3	413.9	-	306.9	481	367	413.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C3-525AXSP04	371.6	574.3	441	494.2	-	371.9	572.1	440	493	-	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C3-532AXSP04	347.1	541.4	413.9	465.5	905.2	347.6	539.2	413	464.3	899.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C3-625AXSP04	398.2	610.2	471.1	526.8	1002.6	399	608.1	470.8	525.6	995.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C3-632AXSP04	377.1	584.1	448.7	503.3	967.1	377.9	581.7	448.3	501.9	960.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C4-425AXSP04	332.8	520.9	397.6	447.3	-	332.9	519.1	397	446.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C4-432AXSP04	306.5	483.4	367.3	413.9	-	306.9	481	367	413.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C4-525AXSP04	371.6	574.3	441	494.2	-	371.9	572.1	440	493	-	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C4-532AXSP04	347.1	541.4	413.9	465.5	905.2	347.6	539.2	413	464.3	899.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C4-625AXSP04	398.2	610.2	471.1	526.8	1002.6	399	608.1	470.8	525.6	995.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C4-632AXSP04	377.1	584.1	448.7	503.3	967.1	377.9	581.7	448.3	501.9	960.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C5-425AXSP04	332.8	520.9	397.6	447.3	-	332.9	519.1	397	446.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C5-432AXSP04	306.5	483.4	367.3	413.9	-	306.9	481	367	413.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C5-525AXSP04	371.6	574.3	441	494.2	-	371.9	572.1	440	493	-	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C5-532AXSP04	347.1	541.4	413.9	465.5	905.2	347.6	539.2	413	464.3	899.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C5-625AXSP04	398.2	610.2	471.1	526.8	1002.6	399	608.1	470.8	525.6	995.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C5-632AXSP04	377.1	584.1	448.7	503.3	967.1	377.9	581.7	448.3	501.9	960.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C8-425AXSP04	332.8	520.9	397.6	447.3	-	332.9	519.1	397	446.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C8-432AXSP04	306.5	483.4	367.3	413.9	-	306.9	481	367	413.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C8-525AXSP04	371.6	574.3	441	494.2	-	371.9	572.1	440	493	-	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C8-532AXSP04	347.1	541.4	413.9	465.5	905.2	347.6	539.2	413	464.3	899.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C8-625AXSP04	398.2	610.2	471.1	526.8	1002.6	399	608.1	470.8	525.6	995.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C8-632AXSP04	377.1	584.1	448.7	503.3	967.1	377.9	581.7	448.3	501.9	960.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C9-425AXSP04	332.8	520.9	397.6	447.3	-	332.9	519.1	397	446.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C9-432AXSP04	306.5	483.4	367.3	413.9	-	306.9	481	367	413.4	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750C9-525AXSP04	371.6	574.3	441	494.2	-	371.9	572.1	440	493	-	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C9-532AXSP04	347.1	541.4	413.9	465.5	905.2	347.6	539.2	413	464.3	899.8	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750C9-625AXSP04	398.2	610.2	471.1	526.8	1002.6	399	608.1	470.8	525.6	995.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750C9-632AXSP04	377.1	584.1	448.7	503.3	967.1	377.9	581.7	448.3	501.9	960.4	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K2-425AXSP04	321.9	503.6	384.4	432.1	-	322.6	501.9	383.8	431.3	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750K2-432AXSP04	297.1	467.4	355.8	401.5	-	297.4	466	355.2	400.1	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750K2-525AXSP04	358.7	554.3	425.5	476.7	918.3	359	552.1	424.6	475.5	912.1	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750K2-532AXSP04	335.4	523	400.5	450.1	873.3	335.9	521.1	399.7	448.4	868.5	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750K2-625AXSP04	384.3	588.1	454.5	508.1	964.3	384.8	585.6	453.9	506.6	957.9	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K2-632AXSP04	364.3	563.2	433.2	485.7	931.6	364.4	560.8	432.1	484.3	925	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K3-425AXSP04	321.9	503.6	384.4	432.1	-	322.6	501.9	383.8	431.3	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750K3-432AXSP04	297.1	467.4	355.8	401.5	-	297.4	466	355.2	400.1	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750K3-525AXSP04	358.7	554.3	425.5	476.7	918.3	359	552.1	424.6	475.5	912.1	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750K3-532AXSP04	335.4	523	400.5	450.1	873.3	335.9	521.1	399.7	448.4	868.5	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750K3-625AXSP04	384.3	588.1	454.5	508.1	964.3	384.8	585.6	453.9	506.6	957.9	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K3-632AXSP04	364.3	563.2	433.2	485.7	931.6	364.4	560.8	432.1	484.3	925	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K4-425AXSP04	321.9	503.6	384.4	432.1	-	322.6	501.9	383.8	431.3	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750K4-432AXSP04	297.1	467.4	355.8	401.5	-	297.4	466	355.2	400.1	-	451	18.7	3"	361	12.3	3"	541	22.9	4"
EAW-VD155SPK750K4-525AXSP04	358.7	554.3	425.5	476.7	918.3	359	552.1	424.6	475.5	912.1	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750K4-532AXSP04	335.4	523	400.5	450.1	873.3	335.9	521.1	399.7	448.4	868.5	564	17	4"	451	13.6	3"	676	23.9	4"
EAW-VD155SPK750K4-625AXSP04	384.3	588.1	454.5	508.1	964.3	384.8	585.6	453.9	506.6	957.9	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K4-632AXSP04	364.3	563.2	433.2	485.7	931.6	364.4	560.8	432.1	484.3	925	676	17.8	4"	541	11.7	4"	812	25	4"
EAW-VD155SPK750K5-425AXSP04	321.9	503.6	384.4	432.1	-	322.6	501.9	383.8	431.3	-	451	18.7	3"	361	12.3	3"	541	22.9	

EAW-VD155SZB370C5-525AXSP06	351.7	532.3	413	460.4	-	349.9	527.5	409.9	456.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370C5-532AXSP06	329.7	504.1	389	434.7	829.4	328.1	499.4	386	431.3	819.4	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370C8-625AXSP06	377.3	565.2	441.1	489.9	912.1	375.1	560	437.6	486	901.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370C5-632AXSP06	358	542.3	420.8	468.9	882.9	356.1	537.3	417.5	465.1	872.7	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370C8-425AXSP06	315.5	484.2	373.3	417.8	-	314.2	479.9	370.6	414.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370C8-432AXSP06	291.8	451.3	346.1	388.7	-	290.4	447.6	343.9	385.4	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370C8-525AXSP06	351.7	532.3	413	460.4	-	349.9	527.5	409.9	456.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370C8-532AXSP06	329.7	504.1	389	434.7	829.4	328.1	499.4	386	431.3	819.4	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370C8-625AXSP06	377.3	565.2	441.1	489.9	912.1	375.1	560	437.6	486	901.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370C8-632AXSP06	358	542.3	420.8	468.9	882.9	356.1	537.3	417.5	465.1	872.7	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K2-425AXSP06	304.2	466	359.2	401.8	-	302.5	462.1	356.7	398.9	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K2-432AXSP06	282	435.3	334.4	374.6	-	280.7	431.8	332.3	372.1	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K2-525AXSP06	337.6	510.9	396.3	441.7	832.1	335.8	506.3	393.3	438.2	822.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K2-532AXSP06	317.2	484.2	374.1	417.9	796	315.7	479.9	371.3	414.7	786.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K2-625AXSP06	361.6	541.1	422.7	469.3	871.7	359.5	535.5	418.8	465	862	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K2-632AXSP06	344.2	520	404	450	846.1	341.8	515.2	400.7	446.3	836.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K4-425AXSP06	304.2	466	359.2	401.8	-	302.5	462.1	356.7	398.9	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K4-432AXSP06	282	435.3	334.4	374.6	-	280.7	431.8	332.3	372.1	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K4-525AXSP06	337.6	510.9	396.3	441.7	832.1	335.8	506.3	393.3	438.2	822.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K4-532AXSP06	317.2	484.2	374.1	417.9	796	315.7	479.9	371.3	414.7	786.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K4-625AXSP06	361.6	541.1	422.7	469.3	871.7	359.5	535.5	418.8	465	862	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K4-632AXSP06	344.2	520	404	450	846.1	341.8	515.2	400.7	446.3	836.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K5-425AXSP06	304.2	466	359.2	401.8	-	302.5	462.1	356.7	398.9	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K5-432AXSP06	282	435.3	334.4	374.6	-	280.7	431.8	332.3	372.1	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K5-525AXSP06	337.6	510.9	396.3	441.7	832.1	335.8	506.3	393.3	438.2	822.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K5-532AXSP06	317.2	484.2	374.1	417.9	796	315.7	479.9	371.3	414.7	786.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K5-625AXSP06	361.6	541.1	422.7	469.3	871.7	359.5	535.5	418.8	465	862	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K5-632AXSP06	344.2	520	404	450	846.1	341.8	515.2	400.7	446.3	836.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K8-425AXSP06	304.2	466	359.2	401.8	-	302.5	462.1	356.7	398.9	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K8-432AXSP06	282	435.3	334.4	374.6	-	280.7	431.8	332.3	372.1	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB370K8-525AXSP06	337.6	510.9	396.3	441.7	832.1	335.8	506.3	393.3	438.2	822.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K8-532AXSP06	317.2	484.2	374.1	417.9	796	315.7	479.9	371.3	414.7	786.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB370K8-625AXSP06	361.6	541.1	422.7	469.3	871.7	359.5	535.5	418.8	465	862	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB370K8-632AXSP06	344.2	520	404	450	846.1	341.8	515.2	400.7	446.3	836.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400B3-425AXSP06	307.9	472.7	364.2	407.4	-	306.7	468.1	361.7	404.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400B3-432AXSP06	285.4	440.9	338.4	379.8	-	284.1	437.4	336.4	377.4	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400B3-525AXSP06	342.2	518.1	401.7	447.7	845	340.5	512.8	398.7	444.3	835.5	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400B3-532AXSP06	321.5	491.1	379.3	423.7	807.5	320.1	486.8	376.5	420.6	798.3	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400B3-625AXSP06	366	547.9	427.3	475.1	882.7	364.2	542.6	424.3	471.1	873.6	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400B3-632AXSP06	348.9	527.3	409.4	456.1	858	346.5	522.5	406.3	452.5	848.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400C3-425AXSP06	315.5	484.2	373.3	417.8	-	314.2	479.9	370.6	414.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400C3-432AXSP06	291.8	451.3	346.1	388.7	-	290.4	447.6	343.9	385.4	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400C3-525AXSP06	351.7	532.3	413	460.4	-	349.9	527.5	409.9	456.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400C3-532AXSP06	329.7	504.1	389	434.7	829.4	328.1	499.4	386	431.3	819.4	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400C3-625AXSP06	377.3	565.2	441.1	489.9	912.1	375.1	560	437.6	486	901.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400C3-632AXSP06	358	542.3	420.8	468.9	882.9	356.1	537.3	417.5	465.1	872.7	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400C9-425AXSP06	315.5	484.2	373.3	417.8	-	314.2	479.9	370.6	414.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400C9-432AXSP06	291.8	451.3	346.1	388.7	-	290.4	447.6	343.9	385.4	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400C9-525AXSP06	351.7	532.3	413	460.4	-	349.9	527.5	409.9	456.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400C9-532AXSP06	329.7	504.1	389	434.7	829.4	328.1	499.4	386	431.3	819.4	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400C9-625AXSP06	377.3	565.2	441.1	489.9	912.1	375.1	560	437.6	486	901.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400C9-632AXSP06	358	542.3	420.8	468.9	882.9	356.1	537.3	417.5	465.1	872.7	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400K3-425AXSP06	304.2	466	359.2	401.8	-	302.5	462.1	356.7	398.9	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400K3-432AXSP06	282	435.3	334.4	374.6	-	280.7	431.8	332.3	372.1	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400K3-525AXSP06	337.6	510.9	396.3	441.7	832.1	335.8	506.3	393.3	438.2	822.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400K3-532AXSP06	317.2	484.2	374.1	417.9	796	315.7	479.9	371.3	414.7	786.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400K3-625AXSP06	361.6	541.1	422.7	469.3	871.7	359.5	535.5	418.8	465	862	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400K3-632AXSP06	344.2	520	404	450	846.1	341.8	515.2	400.7	446.3	836.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400K9-425AXSP06	304.2	466	359.2	401.8	-	302.5	462.1	356.7	398.9	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400K9-432AXSP06	282	435.3	334.4	374.6	-	280.7	431.8	332.3	372.1	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB400K9-525AXSP06	337.6	510.9	396.3	441.7	832.1	335.8	506.3	393.3	438.2	822.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400K9-532AXSP06	317.2	484.2	374.1	417.9	796	315.7	479.9	371.3	414.7	786.7	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB400K9-625AXSP06	361.6	541.1	422.7	469.3	871.7	359.5	535.5	418.8	465	862	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB400K9-632AXSP06	344.2	520	404	450	846.1	341.8	515.2	400.7	446.3	836.3	609	22.8	4"	487	18	3"</			

EAW-VD15SSZB550C8-432AXSP06	326	505.7	387.3	434.9	-	324.3	502	385.2	431.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550C8-525AXSP06	395.8	602.4	465.8	520.7	-	394.2	597.4	462.7	516.3	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550C8-532AXSP06	369.8	567.4	436.8	489.6	-	367.8	562.7	433.9	485.5	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550C8-625AXSP06	427.6	642.6	500.2	556.7	-	424.9	637.1	496.6	551.9	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550C8-632AXSP06	404.4	613.2	475	529.9	1003.4	402	608	471.7	526	992.4	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550C9-425AXSP04	338.9	532.2	406.2	456.6	889.9	338.8	529	405.2	454.5	881.4	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD15SSZB550C9-432AXSP06	326	505.7	387.3	434.9	-	324.3	502	385.2	431.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550C9-525AXSP06	395.8	602.4	465.8	520.7	-	394.2	597.4	462.7	516.3	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550C9-532AXSP06	369.8	567.4	436.8	489.6	-	367.8	562.7	433.9	485.5	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550C9-625AXSP06	427.6	642.6	500.2	556.7	-	424.9	637.1	496.6	551.9	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550C9-632AXSP06	404.4	613.2	475	529.9	1003.4	402	608	471.7	526	992.4	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K2-425AXSP06	339.3	521.6	401.7	450	-	337.8	517.8	399.4	446.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K2-432AXSP06	313.3	485.8	372.7	418.2	-	312.3	482.4	370.2	415.3	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K2-525AXSP06	378.2	574.6	444.3	496.4	-	376.1	569.2	442	493	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K2-532AXSP06	354.4	542.8	418.4	468.1	-	352.7	538.5	415.8	465	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K2-625AXSP06	406.6	610.2	475.5	529.1	988.1	404.7	605.2	472.2	524.7	976.8	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K2-632AXSP06	385.9	585.1	453.2	505.3	955.2	383.7	579.5	450.1	501.7	944.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K3-425AXSP06	339.3	521.6	401.7	450	-	337.8	517.8	399.4	446.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K3-432AXSP06	313.3	485.8	372.7	418.2	-	312.3	482.4	370.2	415.3	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K3-525AXSP06	378.2	574.6	444.3	496.4	-	376.1	569.2	442	493	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K3-532AXSP06	354.4	542.8	418.4	468.1	-	352.7	538.5	415.8	465	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K3-625AXSP06	406.6	610.2	475.5	529.1	988.1	404.7	605.2	472.2	524.7	976.8	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K3-632AXSP06	385.9	585.1	453.2	505.3	955.2	383.7	579.5	450.1	501.7	944.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K4-425AXSP06	339.3	521.6	401.7	450	-	337.8	517.8	399.4	446.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K4-432AXSP06	313.3	485.8	372.7	418.2	-	312.3	482.4	370.2	415.3	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K4-525AXSP06	378.2	574.6	444.3	496.4	-	376.1	569.2	442	493	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K4-532AXSP06	354.4	542.8	418.4	468.1	-	352.7	538.5	415.8	465	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K4-625AXSP06	406.6	610.2	475.5	529.1	988.1	404.7	605.2	472.2	524.7	976.8	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K4-632AXSP06	385.9	585.1	453.2	505.3	955.2	383.7	579.5	450.1	501.7	944.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K5-425AXSP06	339.3	521.6	401.7	450	-	337.8	517.8	399.4	446.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K5-432AXSP06	313.3	485.8	372.7	418.2	-	312.3	482.4	370.2	415.3	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K5-525AXSP06	378.2	574.6	444.3	496.4	-	376.1	569.2	442	493	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K5-532AXSP06	354.4	542.8	418.4	468.1	-	352.7	538.5	415.8	465	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K5-625AXSP06	406.6	610.2	475.5	529.1	988.1	404.7	605.2	472.2	524.7	976.8	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K5-632AXSP06	385.9	585.1	453.2	505.3	955.2	383.7	579.5	450.1	501.7	944.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K8-425AXSP06	339.3	521.6	401.7	450	-	337.8	517.8	399.4	446.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K8-432AXSP06	313.3	485.8	372.7	418.2	-	312.3	482.4	370.2	415.3	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K8-525AXSP06	378.2	574.6	444.3	496.4	-	376.1	569.2	442	493	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K8-532AXSP06	354.4	542.8	418.4	468.1	-	352.7	538.5	415.8	465	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K8-625AXSP06	406.6	610.2	475.5	529.1	988.1	404.7	605.2	472.2	524.7	976.8	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K8-632AXSP06	385.9	585.1	453.2	505.3	955.2	383.7	579.5	450.1	501.7	944.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K9-425AXSP06	339.3	521.6	401.7	450	-	337.8	517.8	399.4	446.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K9-432AXSP06	313.3	485.8	372.7	418.2	-	312.3	482.4	370.2	415.3	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550K9-525AXSP06	378.2	574.6	444.3	496.4	-	376.1	569.2	442	493	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K9-532AXSP06	354.4	542.8	418.4	468.1	-	352.7	538.5	415.8	465	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550K9-625AXSP06	406.6	610.2	475.5	529.1	988.1	404.7	605.2	472.2	524.7	976.8	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550K9-632AXSP06	385.9	585.1	453.2	505.3	955.2	383.7	579.5	450.1	501.7	944.9	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550R3-425AXSP04	334	523.9	400.1	449.7	875.6	334.1	520.4	398.9	448.1	868.1	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD15SSZB550R3-432AXSP06	322.1	499.1	382.5	429.4	-	320.6	495.9	380.8	426.6	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD15SSZB550R3-525AXSP06	388.4	590.7	457.1	510	-	387	586.2	454.2	506.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550R3-532AXSP06	363.9	557.9	429.7	481.6	-	362.2	553.7	427.2	477.9	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB550R3-625AXSP06	417.8	627.6	488.8	543.9	-	415.7	623	485.2	539.9	1007.1	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB550R3-632AXSP06	396.2	601.4	466.1	519.8	983.5	394.7	596.6	463	516.3	973.3	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB750C2-425AXSP04	363.6	570.4	435.5	490.1	957.9	364.1	567.9	434.5	487.9	950.2	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD15SSZB750C2-432AXSP04	333.9	529.3	402.2	453.6	893	334.5	526.3	401.6	451.8	885.8	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD15SSZB750C2-525AXSP06	423.6	646.5	499.6	558.1	-	422	642.1	496.3	555.1	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB750C2-532AXSP06	395.6	609	468.4	524.7	-	394.1	604.8	465.9	521.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB750C2-625AXSP06	457	689	534.7	596.3	-	454.9	683.4	531.8	592.1	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB750C2-632AXSP06	432.5	657.5	509	568.2	-	430.6	653	505.5	564.2	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB750C3-425AXSP04	363.6	570.4	435.5	490.1	957.9	364.1	567.9	434.5	487.9	950.2	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD15SSZB750C3-432AXSP04	333.9	529.3	402.2	453.6	893	334.5	526.3	401.6	451.8	885.8	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD15SSZB750C3-525AXSP06	423.6	646.5	499.6	558.1	-	422	642.1	496.3	555.1	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB750C3-532AXSP06	395.6	609	468.4	524.7	-	394.1	604.8	465.9	521.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD15SSZB750C3-625AXSP06	457	689	534.7	596.3	-	454.9	683.4	531.8	592.1	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD15SSZB750C3-632AXSP06	432.5	657.5	509	568.2	-	430.6	653	505.5	564.2										

EAW-VD155SZB750K4-425AXSP04	351.7	551.6	421	473.6	923.7	352.2	549.2	420	472.2	917.6	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD155SZB750K4-432AXSP06	338.4	526	402.2	451.9	-	337.1	522.1	400.7	449.2	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB750K4-525AXSP06	409.1	623.4	481.6	538.5	-	407.4	619.1	479	534.7	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K4-532AXSP06	382.9	588.4	453.1	507.4	-	381.5	583.6	450.1	503.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K4-625AXSP06	440.3	662.2	515.1	573.5	-	438.4	658	512.5	569.7	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K4-632AXSP06	417.2	634.4	490.9	548.6	-	415.8	629.7	488	544.5	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K5-425AXSP04	351.7	551.6	421	473.6	923.7	352.2	549.2	420	472.2	917.6	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD155SZB750K5-432AXSP06	338.4	526	402.2	451.9	-	337.1	522.1	400.7	449.2	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB750K5-525AXSP06	409.1	623.4	481.6	538.5	-	407.4	619.1	479	534.7	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K5-532AXSP06	382.9	588.4	453.1	507.4	-	381.5	583.6	450.1	503.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K5-625AXSP06	440.3	662.2	515.1	573.5	-	438.4	658	512.5	569.7	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K5-632AXSP06	417.2	634.4	490.9	548.6	-	415.8	629.7	488	544.5	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K8-425AXSP04	351.7	551.6	421	473.6	923.7	352.2	549.2	420	472.2	917.6	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD155SZB750K8-432AXSP06	338.4	526	402.2	451.9	-	337.1	522.1	400.7	449.2	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB750K8-525AXSP06	409.1	623.4	481.6	538.5	-	407.4	619.1	479	534.7	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K8-532AXSP06	382.9	588.4	453.1	507.4	-	381.5	583.6	450.1	503.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K8-625AXSP06	440.3	662.2	515.1	573.5	-	438.4	658	512.5	569.7	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K8-632AXSP06	417.2	634.4	490.9	548.6	-	415.8	629.7	488	544.5	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K9-425AXSP04	351.7	551.6	421	473.6	923.7	352.2	549.2	420	472.2	917.6	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD155SZB750K9-432AXSP06	338.4	526	402.2	451.9	-	337.1	522.1	400.7	449.2	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB750K9-525AXSP06	409.1	623.4	481.6	538.5	-	407.4	619.1	479	534.7	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K9-532AXSP06	382.9	588.4	453.1	507.4	-	381.5	583.6	450.1	503.8	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750K9-625AXSP06	440.3	662.2	515.1	573.5	-	438.4	658	512.5	569.7	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750K9-632AXSP06	417.2	634.4	490.9	548.6	-	415.8	629.7	488	544.5	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750R3-425AXSP04	344.3	540.2	412	464.1	903.8	344.7	537	411.7	461.9	896.6	609	15.9	4"	487	13.4	3"	730	22.4	4"
EAW-VD155SZB750R3-432AXSP06	331.6	514.9	394.1	442.6	-	330.9	511.9	392.5	440.7	-	406	23.6	3"	325	15.6	3"	487	33.2	3"
EAW-VD155SZB750R3-525AXSP06	400.3	609.4	471.2	526	-	398.6	604.4	468.6	522.9	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750R3-532AXSP06	374.6	575.2	443.2	496.2	-	373.8	571.3	440.9	493.4	-	507	25.3	3"	406	16.7	3"	609	31.1	4"
EAW-VD155SZB750R3-625AXSP06	429.5	646.5	502.5	560.1	-	428.3	641.5	499.9	556.4	-	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZB750R3-632AXSP06	408.3	620.2	480.3	535.8	1015.1	406.3	614.9	476.8	531.9	1005.1	609	22.8	4"	487	18	3"	730	32	4"
EAW-VD155SZK017G7-425AXSP04	457.7	717.3	547.1	615.6	-	457.2	712.2	544.3	612.3	-	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK017G7-432AXSP04	418.1	659.3	501.2	565.5	-	417.9	655.3	499.3	561.9	-	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK017G7-525AXSP04	516.8	799.3	613.7	688.2	-	515.3	794.3	610.9	684.9	-	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD155SZK017G7-532AXSP04	476.5	744.7	569.6	639.9	1246.9	476.4	740.4	567.4	637.1	1235.1	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD155SZK017G7-625AXSP04	565.5	867	668.3	747.8	1426.2	564	861	665.7	743.7	1412.5	913	16.4	(2) 4"	730	13.2	4"	1096	23	(2) 4"
EAW-VD155SZK017G7-632AXSP04	528.1	818	627.7	704.4	1355.9	527.2	812.6	625.6	700.7	1342.8	913	16.4	(2) 4"	730	13.2	4"	1096	23	(2) 4"
EAW-VD155SZK370C2-425AXSP06	331.9	506.9	391.2	437.4	-	329.6	501.9	387.9	433	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C2-432AXSP06	306.9	472.1	363	407.2	-	305	467.7	360.3	403.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C2-525AXSP06	369.8	557.5	432.9	482.2	-	366.8	551.1	428.9	477.8	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C2-532AXSP06	346.7	527	407.6	455.1	-	344.1	521.6	404	451.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C2-625AXSP06	397.1	591.5	462.4	513.2	951.5	394.3	584.9	458.2	508	938.9	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C2-632AXSP06	377	567.4	441.1	491.2	920.4	374.3	560.7	437	486.5	908.5	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C4-425AXSP06	331.9	506.9	391.2	437.4	-	329.6	501.9	387.9	433	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C4-432AXSP06	306.9	472.1	363	407.2	-	305	467.7	360.3	403.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C4-525AXSP06	369.8	557.5	432.9	482.2	-	366.8	551.1	428.9	477.8	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C4-532AXSP06	346.7	527	407.6	455.1	-	344.1	521.6	404	451.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C4-625AXSP06	397.1	591.5	462.4	513.2	951.5	394.3	584.9	458.2	508	938.9	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C4-632AXSP06	377	567.4	441.1	491.2	920.4	374.3	560.7	437	486.5	908.5	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C5-425AXSP06	331.9	506.9	391.2	437.4	-	329.6	501.9	387.9	433	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C5-432AXSP06	306.9	472.1	363	407.2	-	305	467.7	360.3	403.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C5-525AXSP06	369.8	557.5	432.9	482.2	-	366.8	551.1	428.9	477.8	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C5-532AXSP06	346.7	527	407.6	455.1	-	344.1	521.6	404	451.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C5-625AXSP06	397.1	591.5	462.4	513.2	951.5	394.3	584.9	458.2	508	938.9	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C5-632AXSP06	377	567.4	441.1	491.2	920.4	374.3	560.7	437	486.5	908.5	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C8-425AXSP06	331.9	506.9	391.2	437.4	-	329.6	501.9	387.9	433	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C8-432AXSP06	306.9	472.1	363	407.2	-	305	467.7	360.3	403.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370C8-525AXSP06	369.8	557.5	432.9	482.2	-	366.8	551.1	428.9	477.8	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C8-532AXSP06	346.7	527	407.6	455.1	-	344.1	521.6	404	451.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370C8-625AXSP06	397.1	591.5	462.4	513.2	951.5	394.3	584.9	458.2	508	938.9	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370C8-632AXSP06	377	567.4	441.1	491.2	920.4	374.3	560.7	437	486.5	908.5	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK370K2-425AXSP06	320	488	377	421.4	-	317.9	483.4	374	417.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370K2-432AXSP06	296.4	455.9	351.1	392.9	-	294.6	451.7	347.8	389.8	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK370K2-525AXSP06	355.1	534.7	415.5	462.7	-	352.8	528.7	411.9	458.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370K2-532AXSP06	334.1	507.1	392.6	438.2	830	331.6	502.1	389.3	433.8	819.6	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK370K2-625AXSP06	380.6	566.4	443.1	491.7	908.6	377.5	560	438.6	486.7	896.7	609	25	4"	487	19.4</				

EAW-VD155SZK400C9-632AXSP06	377	567.4	441.1	491.2	920.4	374.3	560.7	437	486.5	908.5	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK400K3-425AXSP06	320	488	377	421.4	-	317.9	483.4	374	417.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK400K3-432AXSP06	296.4	455.9	351.1	392.9	-	294.6	451.7	347.8	389.8	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK400K3-525AXSP06	355.1	534.7	415.5	462.7	-	352.8	528.7	411.9	458.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK400K3-532AXSP06	334.1	507.1	392.6	438.2	830	331.6	502.1	389.3	433.8	819.6	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK400K3-625AXSP06	380.6	566.4	443.1	491.7	908.6	377.5	560	438.6	486.7	896.7	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK400K3-632AXSP06	362.1	544.3	423.6	471.5	881.3	359.1	538.1	419.8	466.6	870.3	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK400K9-425AXSP06	320	488	377	421.4	-	317.9	483.4	374	417.3	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK400K9-432AXSP06	296.4	455.9	351.1	392.9	-	294.6	451.7	347.8	389.8	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK400K9-525AXSP06	355.1	534.7	415.5	462.7	-	352.8	528.7	411.9	458.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK400K9-532AXSP06	334.1	507.1	392.6	438.2	830	331.6	502.1	389.3	433.8	819.6	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK400K9-625AXSP06	380.6	566.4	443.1	491.7	908.6	377.5	560	438.6	486.7	896.7	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK400K9-632AXSP06	362.1	544.3	423.6	471.5	881.3	359.1	538.1	419.8	466.6	870.3	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK400R3-425AXSP06	326.4	498.9	385.2	430.6	-	324.8	493.6	382.2	426.6	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK400R3-432AXSP06	302.8	466.2	358.2	401.6	-	301.2	461.5	355.7	398.1	-	406	25.8	3"	325	17	3"	487	36.2	3"
EAW-VD155SZK400R3-525AXSP06	362.5	546.2	424.3	472.6	-	360.4	540.3	420.7	468.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK400R3-532AXSP06	341.2	518.3	401.1	447.8	-	338.9	513.4	397.8	443.5	839.5	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK400R3-625AXSP06	388.8	578.2	452.1	501.8	928.9	385.8	571.9	448.3	496.9	918	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK400R3-632AXSP06	369.7	556.1	433.1	481.5	901.7	367.3	550.6	428.8	477.3	890.8	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK500B3-425AXSP04	344	534.8	410	460.1	889.3	342.8	531.1	408	457.6	880.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK500B3-432AXSP04	317.3	497.9	380.2	427.3	833.4	316.6	494.8	378	425.4	825.3	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK500B3-525AXSP06	397.8	601.1	466.4	520	-	395.2	595.8	462.9	516	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK500B3-532AXSP06	372.8	568.3	439.2	490.8	-	370.5	563.2	435.9	487	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK500B3-625AXSP06	427.3	638.4	498.3	553.4	-	424.4	632	493.9	548.5	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK500B3-632AXSP06	406	612.4	475.9	530.2	995.9	403.2	606	471.5	525.3	984.4	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C2-425AXSP04	358.7	558.9	427.8	480.4	930.8	358	554.9	426.3	477.7	921.1	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C2-432AXSP04	329.7	518.7	395.4	445.5	869.6	329.5	514.3	393.6	442.5	860.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C2-525AXSP06	416.9	631.9	489.7	546.2	-	414.5	625.8	485.6	541.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C2-532AXSP06	389.4	594.7	458.9	513.1	-	386.8	589.1	455.3	509	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C2-625AXSP06	450.3	673.7	525.3	584.3	-	447	667.3	520.9	578.7	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C2-632AXSP06	425.4	643.5	499.5	556.8	-	422.8	636.3	494.5	551.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C3-425AXSP04	358.7	558.9	427.8	480.4	930.8	358	554.9	426.3	477.7	921.1	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C3-432AXSP04	329.7	518.7	395.4	445.5	869.6	329.5	514.3	393.6	442.5	860.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C3-525AXSP06	416.9	631.9	489.7	546.2	-	414.5	625.8	485.6	541.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C3-532AXSP06	389.4	594.7	458.9	513.1	-	386.8	589.1	455.3	509	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C3-625AXSP06	450.3	673.7	525.3	584.3	-	447	667.3	520.9	578.7	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C3-632AXSP06	425.4	643.5	499.5	556.8	-	422.8	636.3	494.5	551.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C4-425AXSP04	358.7	558.9	427.8	480.4	930.8	358	554.9	426.3	477.7	921.1	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C4-432AXSP04	329.7	518.7	395.4	445.5	869.6	329.5	514.3	393.6	442.5	860.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C4-525AXSP06	416.9	631.9	489.7	546.2	-	414.5	625.8	485.6	541.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C4-532AXSP06	389.4	594.7	458.9	513.1	-	386.8	589.1	455.3	509	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C4-625AXSP06	450.3	673.7	525.3	584.3	-	447	667.3	520.9	578.7	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C4-632AXSP06	425.4	643.5	499.5	556.8	-	422.8	636.3	494.5	551.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C5-425AXSP04	358.7	558.9	427.8	480.4	930.8	358	554.9	426.3	477.7	921.1	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C5-432AXSP04	329.7	518.7	395.4	445.5	869.6	329.5	514.3	393.6	442.5	860.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C5-525AXSP06	416.9	631.9	489.7	546.2	-	414.5	625.8	485.6	541.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C5-532AXSP06	389.4	594.7	458.9	513.1	-	386.8	589.1	455.3	509	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C5-625AXSP06	450.3	673.7	525.3	584.3	-	447	667.3	520.9	578.7	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C5-632AXSP06	425.4	643.5	499.5	556.8	-	422.8	636.3	494.5	551.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C8-425AXSP04	358.7	558.9	427.8	480.4	930.8	358	554.9	426.3	477.7	921.1	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C8-432AXSP04	329.7	518.7	395.4	445.5	869.6	329.5	514.3	393.6	442.5	860.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C8-525AXSP06	416.9	631.9	489.7	546.2	-	414.5	625.8	485.6	541.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C8-532AXSP06	389.4	594.7	458.9	513.1	-	386.8	589.1	455.3	509	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C8-625AXSP06	450.3	673.7	525.3	584.3	-	447	667.3	520.9	578.7	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C8-632AXSP06	425.4	643.5	499.5	556.8	-	422.8	636.3	494.5	551.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C9-425AXSP04	358.7	558.9	427.8	480.4	930.8	358	554.9	426.3	477.7	921.1	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C9-432AXSP04	329.7	518.7	395.4	445.5	869.6	329.5	514.3	393.6	442.5	860.4	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550C9-525AXSP06	416.9	631.9	489.7	546.2	-	414.5	625.8	485.6	541.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C9-532AXSP06	389.4	594.7	458.9	513.1	-	386.8	589.1	455.3	509	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550C9-625AXSP06	450.3	673.7	525.3	584.3	-	447	667.3	520.9	578.7	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550C9-632AXSP06	425.4	643.5	499.5	556.8	-	422.8	636.3	494.5	551.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD155SZK550K2-425AXSP04	344.6	535.9	410.8	461	891.3	344.1	532.3	408.9	458.6	883.7	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550K2-432AXSP04	318	499	381	429.1	835.5	317.3	496	379.5	426.4	828.7	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD155SZK550K2-525AXSP06	398.6	603.2	468	521.7	-	396.5	596.9	463.8	517	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD155SZK550K2-532AXSP06	374.1	570.3	440.7	492.5															

EAW-VD1555ZK550R3-625AXSP06	441.5	660.1	514.9	572	-	438.5	653.5	510.3	566.8	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK550R3-632AXSP06	418.8	632.3	490.3	546.5	-	416.1	625.8	486.6	542.2	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C2-425AXSP06	386.2	602.1	460.3	517.4	1005.3	386	598.5	458.5	515.1	995.9	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C2-432AXSP04	354.9	557.7	425.3	479	938.1	354.6	554.9	424.1	476.5	929.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C2-525AXSP06	430.5	664.3	511	572.5	1095.9	429.7	659	508.5	568.8	1085.6	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750C2-532AXSP06	418.3	640.8	494	552.9	-	416.7	635.5	490.7	549.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750C2-625AXSP06	483.5	725.6	564.8	628.7	-	480.7	719	561.1	623.6	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C2-632AXSP06	457.6	692.9	536.7	598.7	-	454.9	687.1	533	594.4	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C3-425AXSP04	386.2	602.1	460.3	517.4	1005.3	386	598.5	458.5	515.1	995.9	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C3-432AXSP04	354.9	557.7	425.3	479	938.1	354.6	554.9	424.1	476.5	929.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C3-525AXSP04	430.5	664.3	511	572.5	1095.9	429.7	659	508.5	568.8	1085.6	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750C3-532AXSP06	418.3	640.8	494	552.9	-	416.7	635.5	490.7	549.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750C3-625AXSP06	483.5	725.6	564.8	628.7	-	480.7	719	561.1	623.6	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C3-632AXSP06	457.6	692.9	536.7	598.7	-	454.9	687.1	533	594.4	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C4-425AXSP06	386.2	602.1	460.3	517.4	1005.3	386	598.5	458.5	515.1	995.9	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C4-432AXSP04	354.9	557.7	425.3	479	938.1	354.6	554.9	424.1	476.5	929.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C4-525AXSP04	430.5	664.3	511	572.5	1095.9	429.7	659	508.5	568.8	1085.6	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750C4-532AXSP06	418.3	640.8	494	552.9	-	416.7	635.5	490.7	549.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750C4-625AXSP06	483.5	725.6	564.8	628.7	-	480.7	719	561.1	623.6	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C4-632AXSP06	457.6	692.9	536.7	598.7	-	454.9	687.1	533	594.4	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C5-425AXSP04	386.2	602.1	460.3	517.4	1005.3	386	598.5	458.5	515.1	995.9	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C5-432AXSP04	354.9	557.7	425.3	479	938.1	354.6	554.9	424.1	476.5	929.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C5-525AXSP04	430.5	664.3	511	572.5	1095.9	429.7	659	508.5	568.8	1085.6	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750C5-532AXSP06	418.3	640.8	494	552.9	-	416.7	635.5	490.7	549.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750C5-625AXSP06	483.5	725.6	564.8	628.7	-	480.7	719	561.1	623.6	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C5-632AXSP06	457.6	692.9	536.7	598.7	-	454.9	687.1	533	594.4	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C8-425AXSP06	386.2	602.1	460.3	517.4	1005.3	386	598.5	458.5	515.1	995.9	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C8-432AXSP04	354.9	557.7	425.3	479	938.1	354.6	554.9	424.1	476.5	929.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C8-525AXSP06	430.5	664.3	511	572.5	1095.9	429.7	659	508.5	568.8	1085.6	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750C8-532AXSP06	418.3	640.8	494	552.9	-	416.7	635.5	490.7	549.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750C8-625AXSP06	483.5	725.6	564.8	628.7	-	480.7	719	561.1	623.6	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C8-632AXSP06	457.6	692.9	536.7	598.7	-	454.9	687.1	533	594.4	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C9-425AXSP04	386.2	602.1	460.3	517.4	1005.3	386	598.5	458.5	515.1	995.9	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C9-432AXSP04	354.9	557.7	425.3	479	938.1	354.6	554.9	424.1	476.5	929.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750C9-525AXSP06	430.5	664.3	511	572.5	1095.9	429.7	659	508.5	568.8	1085.6	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750C9-532AXSP06	418.3	640.8	494	552.9	-	416.7	635.5	490.7	549.1	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750C9-625AXSP06	483.5	725.6	564.8	628.7	-	480.7	719	561.1	623.6	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750C9-632AXSP06	457.6	692.9	536.7	598.7	-	454.9	687.1	533	594.4	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K2-425AXSP04	373.8	581.8	445.4	500.3	971.7	373.7	578.5	443.7	498.3	963	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K2-432AXSP04	344.1	540.9	413	464.9	908.5	343.9	538.2	411.1	462.5	900.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K2-525AXSP06	415.4	640	492.8	552	1056.3	414.6	635.9	490.5	549.2	1045.2	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750K2-532AXSP06	405	619.5	478.2	534.1	-	403	614.6	474.4	530.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750K2-625AXSP06	466.2	698.9	544.5	605.1	-	463.3	692.2	540	600	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K2-632AXSP06	441.4	668.5	518.3	578	-	439.4	662	514.7	573.1	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K3-425AXSP04	373.8	581.8	445.4	500.3	971.7	373.7	578.5	443.7	498.3	963	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K3-432AXSP04	344.1	540.9	413	464.9	908.5	343.9	538.2	411.1	462.5	900.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K3-525AXSP06	415.4	640	492.8	552	1056.3	414.6	635.9	490.5	549.2	1045.2	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750K3-532AXSP06	405	619.5	478.2	534.1	-	403	614.6	474.4	530.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750K3-625AXSP06	466.2	698.9	544.5	605.1	-	463.3	692.2	540	600	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K3-632AXSP06	441.4	668.5	518.3	578	-	439.4	662	514.7	573.1	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K4-425AXSP04	373.8	581.8	445.4	500.3	971.7	373.7	578.5	443.7	498.3	963	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K4-432AXSP04	344.1	540.9	413	464.9	908.5	343.9	538.2	411.1	462.5	900.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K4-525AXSP06	415.4	640	492.8	552	1056.3	414.6	635.9	490.5	549.2	1045.2	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750K4-532AXSP06	405	619.5	478.2	534.1	-	403	614.6	474.4	530.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750K4-625AXSP06	466.2	698.9	544.5	605.1	-	463.3	692.2	540	600	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K4-632AXSP06	441.4	668.5	518.3	578	-	439.4	662	514.7	573.1	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K5-425AXSP06	373.8	581.8	445.4	500.3	971.7	373.7	578.5	443.7	498.3	963	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K5-432AXSP06	344.1	540.9	413	464.9	908.5	343.9	538.2	411.1	462.5	900.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K5-525AXSP06	415.4	640	492.8	552	1056.3	414.6	635.9	490.5	549.2	1045.2	755	18.5	4"	604	12.2	4"	906	22.4	(2) 4"
EAW-VD1555ZK750K5-532AXSP06	405	619.5	478.2	534.1	-	403	614.6	474.4	530.6	-	507	27.5	3"	406	18.1	3"	609	34.1	4"
EAW-VD1555ZK750K5-625AXSP06	466.2	698.9	544.5	605.1	-	463.3	692.2	540	600	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K5-632AXSP06	441.4	668.5	518.3	578	-	439.4	662	514.7	573.1	-	609	25	4"	487	19.4	3"	730	35	4"
EAW-VD1555ZK750K8-425AXSP04	373.8	581.8	445.4	500.3	971.7	373.7	578.5	443.7	498.3	963	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K8-432AXSP04	344.1	540.9	413	464.9	908.5	343.9	538.2	411.1	462.5	900.6	609	17.4	4"	487	14.4	3"	730	24.4	4"
EAW-VD1555ZK750K8-525AXSP06	415.4	640	492.8	552	1056.3	414.6	635.9	490.5</											

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6PB370C8-532AXSP04	334.7	519	398.3	447	862.5	334.6	516.4	397	444.7	856.6	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370C8-625AXSP04	380.9	579.9	449.4	501.2	945.4	381.1	576.6	448	499.6	937.8	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370C8-632AXSP04	362.8	557.6	430.3	481.1	917.5	362.9	554.6	428.6	479.1	911.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K2-425AXSP04	309.7	480.8	368.4	413.3	-	309.3	478.4	367.2	411.8	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K2-432AXSP04	286.4	448.1	342.4	384.9	752.2	286.7	446	341.5	383.7	747	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K2-525AXSP04	343	526.8	406.3	454.4	867.2	342.6	523.9	404.7	452.5	860.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K2-532AXSP04	322.2	499.6	383.3	430	829.1	322.1	496.9	382.6	428.3	823.3	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K2-625AXSP04	366.8	557.1	432.1	481.8	907.6	366.6	554	430.3	479.6	900.4	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K2-632AXSP04	348.9	536.2	413.1	463	881.5	348.9	533.2	412	461	874.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K4-425AXSP04	309.7	480.8	368.4	413.3	-	309.3	478.4	367.2	411.8	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K4-432AXSP04	286.4	448.1	342.4	384.9	752.2	286.7	446	341.5	383.7	747	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K4-525AXSP04	343	526.8	406.3	454.4	867.2	342.6	523.9	404.7	452.5	860.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K4-532AXSP04	322.2	499.6	383.3	430	829.1	322.1	496.9	382.6	428.3	823.3	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K4-625AXSP04	366.8	557.1	432.1	481.8	907.6	366.6	554	430.3	479.6	900.4	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K4-632AXSP04	348.9	536.2	413.1	463	881.5	348.9	533.2	412	461	874.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K5-425AXSP04	309.7	480.8	368.4	413.3	-	309.3	478.4	367.2	411.8	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K5-432AXSP04	286.4	448.1	342.4	384.9	752.2	286.7	446	341.5	383.7	747	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K5-525AXSP04	343	526.8	406.3	454.4	867.2	342.6	523.9	404.7	452.5	860.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K5-532AXSP04	322.2	499.6	383.3	430	829.1	322.1	496.9	382.6	428.3	823.3	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K5-625AXSP04	366.8	557.1	432.1	481.8	907.6	366.6	554	430.3	479.6	900.4	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K5-632AXSP04	348.9	536.2	413.1	463	881.5	348.9	533.2	412	461	874.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K8-425AXSP04	309.7	480.8	368.4	413.3	-	309.3	478.4	367.2	411.8	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K8-432AXSP04	286.4	448.1	342.4	384.9	752.2	286.7	446	341.5	383.7	747	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB370K8-525AXSP04	343	526.8	406.3	454.4	867.2	342.6	523.9	404.7	452.5	860.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K8-532AXSP04	322.2	499.6	383.3	430	829.1	322.1	496.9	382.6	428.3	823.3	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB370K8-625AXSP04	366.8	557.1	432.1	481.8	907.6	366.6	554	430.3	479.6	900.4	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB370K8-632AXSP04	348.9	536.2	413.1	463	881.5	348.9	533.2	412	461	874.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400B3-425AXSP04	312.2	484.8	371.4	417.4	-	312.4	482.7	370.4	416.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400B3-432AXSP04	289.7	452.8	345.9	389.5	-	289.7	451	345.2	387.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400B3-525AXSP04	345.5	529.9	408.6	457	873.5	345.5	527.6	407.5	455.6	867.4	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400B3-532AXSP04	325.2	504.4	386.9	434.1	837.3	325.2	501.9	385.7	432.5	830.7	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400B3-625AXSP04	367.3	558.6	433.3	483	910	367.8	555.9	432.3	481.3	903.6	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400B3-632AXSP04	351.3	539.3	415.9	465.6	886.6	351.2	536.8	414.6	464	880.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400C3-425AXSP04	321.1	499.5	382.2	429.7	-	321.4	497.3	381.2	427.7	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400C3-432AXSP04	297.2	465.4	355.1	399.3	-	297.2	462.5	353.3	398.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400C3-525AXSP04	356.8	548.1	422.2	472.3	904.3	356.6	545.2	420.7	470.5	897.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400C3-532AXSP04	334.7	519	398.3	447	862.5	334.6	516.4	397	444.7	856.6	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400C3-625AXSP04	380.9	579.9	449.4	501.2	945.4	381.1	576.6	448	499.6	937.8	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400C3-632AXSP04	362.8	557.6	430.3	481.1	917.5	362.9	554.6	428.6	479.1	911.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400C9-425AXSP04	321.1	499.5	382.2	429.7	-	321.4	497.3	381.2	427.7	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400C9-432AXSP04	297.2	465.4	355.1	399.3	-	297.2	462.5	353.5	398.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400C9-525AXSP04	356.8	548.1	422.2	472.3	904.3	356.6	545.2	420.7	470.5	897.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400C9-532AXSP04	334.7	519	398.3	447	862.5	334.6	516.4	397	444.7	856.6	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400C9-625AXSP04	380.9	579.9	449.4	501.2	945.4	381.1	576.6	448	499.6	937.8	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400C9-632AXSP04	362.8	557.6	430.3	481.1	917.5	362.9	554.6	428.6	479.1	911.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400K3-425AXSP04	309.7	480.8	368.4	413.3	-	309.3	478.4	367.2	411.8	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400K3-432AXSP04	286.4	448.1	342.4	384.9	752.2	286.7	446	341.5	383.7	747	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400K3-525AXSP04	343	526.8	406.3	454.4	867.2	342.6	523.9	404.7	452.5	860.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400K3-532AXSP04	322.2	499.6	383.3	430	829.1	322.1	496.9	382.6	428.3	823.3	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400K3-625AXSP04	366.8	557.1	432.1	481.8	907.6	366.6	554	430.3	479.6	900.4	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400K3-632AXSP04	348.9	536.2	413.1	463	881.5	348.9	533.2	412	461	874.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400K9-425AXSP04	309.7	480.8	368.4	413.3	-	309.3	478.4	367.2	411.8	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400K9-432AXSP04	286.4	448.1	342.4	384.9	752.2	286.7	446	341.5	383.7	747	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400K9-525AXSP04	343	526.8	406.3	454.4	867.2	342.6	523.9	404.7	452.5	860.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400K9-532AXSP04	322.2	499.6	383.3	430	829.1	322.1	496.9	382.6	428.3	823.3	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400K9-625AXSP04	366.8	557.1	432.1	481.8	907.6	366.6	554	430.3	479.6	900.4	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400K9-632AXSP04	348.9	536.2	413.1	463	881.5	348.9	533.2	412	461	874.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400R3-425AXSP04	314.9	488.5	374	420.4	-	314.6	486.3	373.7	419.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400R3-432AXSP04	291.4	456.4	347.9	391.8	-	291.3	453.7	347.1	390.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB400R3-525AXSP04	348.5	535.5	412.8	461.8	881.9	348.8	532.8	411.4	460.1	875.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400R3-532AXSP04	327.5	508.2	389.7	437.2	843.8	327.5	505.7	388.5	435.7	837.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB400R3-625AXSP04	372.3	566.4	439.2	489.7	923	372.3	563.5	437.5	487.8	915.1	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB400R3-632AXSP04	354.4	545	420.3	470.4	896.2	354.5	542.1	418.6	468.5	889.1	676	18.9	4"	541	12.5	4"</			

EAW-VD15S6PB850C9-525AXSP04	400	616.5	473.8	530.9	-	399.6	613.2	472.7	529.4	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850C9-532AXSP04	373.7	580.2	444.8	499.2	-	373.5	577.8	443.7	497.9	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850C9-625AXSP04	429.1	655	506	565.8	1073	429.7	651.6	504.7	563.5	1064.8	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850C9-632AXSP04	406.6	626.2	482.1	539.8	1034.8	406.8	623.6	480.9	538.3	1027.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K2-425AXSP04	342.4	533.6	407.9	458.3	-	342.5	531	407.3	456.6	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K2-432AXSP04	316.3	496	377.9	425.6	-	316.5	494.4	377.5	424.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K2-525AXSP04	380.6	585.4	450.6	504.6	-	380.8	583	449.5	503.2	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K2-532AXSP04	356.6	554	424.8	476.4	922.7	357	551.8	423.9	475.3	917.4	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K2-625AXSP04	407.7	621.3	480.7	537.1	1015.5	408.1	618.6	479.3	534.7	1008.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K2-632AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K3-425AXSP04	342.4	533.6	407.9	458.3	-	342.5	531	407.3	456.6	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K3-432AXSP04	316.3	496	377.9	425.6	-	316.5	494.4	377.5	424.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K3-525AXSP04	380.6	585.4	450.6	504.6	-	380.8	583	449.5	503.2	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K3-532AXSP04	356.6	554	424.8	476.4	922.7	357	551.8	423.9	475.3	917.4	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K4-625AXSP04	407.7	621.3	480.7	537.1	1015.5	408.1	618.6	479.3	534.7	1008.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K4-632AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K4-425AXSP04	342.4	533.6	407.9	458.3	-	342.5	531	407.3	456.6	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K4-432AXSP04	316.3	496	377.9	425.6	-	316.5	494.4	377.5	424.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K4-525AXSP04	380.6	585.4	450.6	504.6	-	380.8	583	449.5	503.2	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K4-532AXSP04	356.6	554	424.8	476.4	922.7	357	551.8	423.9	475.3	917.4	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K5-425AXSP04	407.7	621.3	480.7	537.1	1015.5	408.1	618.6	479.3	534.7	1008.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K5-432AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K5-632AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K8-425AXSP04	342.4	533.6	407.9	458.3	-	342.5	531	407.3	456.6	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K8-432AXSP04	316.3	496	377.9	425.6	-	316.5	494.4	377.5	424.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K8-525AXSP04	380.6	585.4	450.6	504.6	-	380.8	583	449.5	503.2	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K8-532AXSP04	356.6	554	424.8	476.4	922.7	357	551.8	423.9	475.3	917.4	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K8-632AXSP04	407.7	621.3	480.7	537.1	1015.5	408.1	618.6	479.3	534.7	1008.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K9-425AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K9-432AXSP04	342.4	533.6	407.9	458.3	-	342.5	531	407.3	456.6	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K9-632AXSP04	316.3	496	377.9	425.6	-	316.5	494.4	377.5	424.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850K9-525AXSP04	380.6	585.4	450.6	504.6	-	380.8	583	449.5	503.2	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K9-532AXSP04	356.6	554	424.8	476.4	922.7	357	551.8	423.9	475.3	917.4	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850K9-632AXSP04	407.7	621.3	480.7	537.1	1015.5	408.1	618.6	479.3	534.7	1008.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K9-525AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850K9-632AXSP04	387.2	595.8	458.9	514.2	983.3	387.2	593.2	458.2	511.8	976.2	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850R3-425AXSP04	350.5	546.1	417.6	469.5	-	350.8	544.5	416.5	468	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850R3-432AXSP04	323.7	508.5	387.2	436	-	324.2	506.2	386.8	434.7	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB850R3-525AXSP04	389.6	599.9	461.4	516.8	-	390	597.7	460.4	515.6	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850R3-632AXSP04	365.5	567.6	434.8	487.9	-	365.5	564.8	434.1	486.9	939.8	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB850R3-625AXSP04	417.8	636.4	492.7	549.9	1041.9	417.8	633.9	491.4	548.4	1035.3	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB850R3-632AXSP04	396.2	610.3	470.3	526.4	1007.8	396.4	607.8	469.2	524.2	1001	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C2-425AXSP04	378.3	591.4	451.5	508.2	-	379.2	590.4	451.6	507.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C2-432AXSP04	348.9	549.6	418	471.2	-	349.6	547.8	417.5	470.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C2-525AXSP04	421.2	651	500.1	560.7	-	422.3	649.7	499.9	559.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C2-532AXSP04	394.5	614.4	469.8	528.7	-	395	612.9	469.6	527.4	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C2-625AXSP04	451.7	690	533	595.4	-	452.8	687.9	532.9	595.2	1126.9	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C2-632AXSP04	428.9	661.1	508.9	570.1	1095.8	429.9	659.5	508.5	568.7	1090	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C3-425AXSP04	378.3	591.4	451.5	508.2	-	379.2	590.4	451.6	507.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C3-432AXSP04	348.9	549.6	418	471.2	-	349.6	547.8	417.5	470.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C3-525AXSP04	421.2	651	500.1	560.7	-	422.3	649.7	499.9	559.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C3-532AXSP04	394.5	614.4	469.8	528.7	-	395	612.9	469.6	527.4	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C3-625AXSP04	451.7	690	533	595.4	-	452.8	687.9	532.9	595.2	1126.9	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C3-632AXSP04	428.9	661.1	508.9	570.1	1095.8	429.9	659.5	508.5	568.7	1090	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C4-425AXSP04	378.3	591.4	451.5	508.2	-	379.2	590.4	451.6	507.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C4-432AXSP04	348.9	549.6	418	471.2	-	349.6	547.8	417.5	470.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C4-525AXSP04	421.2	651	500.1	560.7	-	422.3	649.7	499.9	559.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C4-532AXSP04	394.5	614.4	469.8	528.7	-	395	612.9	469.6	527.4	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C4-625AXSP04	451.7	690	533	595.4	-	452.8	687.9	532.9	595.2	1126.9	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C4-632AXSP04	428.9	661.1	508.9	570.1	1095.8	429.9	659.5	508.5	568.7	1090	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750C5-425AXSP04	378.3	591.4	451.5	508.2	-	379.2	590.4	451.6	507.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C5-432AXSP04	348.9	549.6	418	471.2	-	349.6	547.8	417.5	470.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750C5-525AXSP04	421.2	651	500.1	560.7	-	422.3	649.7	499.9	559.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C5-532AXSP04	394.5	614.4	469.8	528.7	-	395	612.9	469.6	527.4	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750C5-625AXSP04	451.7	690	533	595.4	-	452.8	687.9	532.9	595.2</										

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6PB750K5-432AXSP04	338.3	531.6	405	456	-	339	531	404.6	455.3	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750K5-525AXSP04	407.2	628.4	483.3	541.6	-	408	626.6	482.7	540	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750K5-532AXSP04	381.8	593.4	454.5	510.3	-	382.2	592	454.2	509.7	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750K5-625AXSP04	436.5	666	515	575.1	1092.9	437.4	664.6	514.6	574.6	1086.6	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750K5-632AXSP04	414.3	638.6	491.4	550.3	1056.1	415	636.7	490.7	549.3	1049.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750K8-425AXSP04	366.3	572.3	436.8	491.4	-	367	570.3	436.8	490.4	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750K8-432AXSP04	338.3	531.6	405	456	-	339	531	404.6	455.3	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750K8-525AXSP04	407.2	628.4	483.3	541.6	-	408	626.6	482.7	540	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750K8-532AXSP04	381.8	593.4	454.5	510.3	-	382.2	592	454.2	509.7	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750K8-625AXSP04	436.5	666	515	575.1	1092.9	437.4	664.6	514.6	574.6	1086.6	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750K8-632AXSP04	414.3	638.6	491.4	550.3	1056.1	415	636.7	490.7	549.3	1049.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750K9-425AXSP04	366.3	572.3	436.8	491.4	-	367	570.3	436.8	490.4	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750K9-432AXSP04	338.3	531.6	405	456	-	339	531	404.6	455.3	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750K9-525AXSP04	407.2	628.4	483.3	541.6	-	408	626.6	482.7	540	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750K9-532AXSP04	381.8	593.4	454.5	510.3	-	382.2	592	454.2	509.7	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750K9-625AXSP04	436.5	666	515	575.1	1092.9	437.4	664.6	514.6	574.6	1086.6	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750K9-632AXSP04	414.3	638.6	491.4	550.3	1056.1	415	636.7	490.7	549.3	1049.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750R3-425AXSP04	366.3	572.3	436.8	491.4	-	367	570.3	436.8	490.4	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750R3-432AXSP04	338.3	531.6	405	456	-	339	531	404.6	455.3	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750R3-525AXSP04	407.2	628.4	483.3	541.6	-	408	626.6	482.7	540	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750R3-532AXSP04	381.8	593.4	454.5	510.3	-	382.2	592	454.2	509.7	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750R3-625AXSP04	436.5	666	515	575.1	1092.9	437.4	664.6	514.6	574.6	1086.6	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750R3-632AXSP04	414.3	638.6	491.4	550.3	1056.1	415	636.7	490.7	549.3	1049.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750R3-632AXSP04	358.4	559.3	428	481.3	-	359	558.1	427.2	480.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750R3-432AXSP04	331.8	521.1	396.7	447.3	-	332.1	519.5	396.6	446.6	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD15S6PB750R3-525AXSP04	398.5	614.2	472	529.7	-	399.2	612.4	471.4	528.1	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750R3-532AXSP04	374.2	580.8	445.3	499.7	-	374.5	579.3	444.1	498.3	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD15S6PB750R3-625AXSP04	426.6	650.3	503.1	561.7	1065.1	427.3	648.7	502.7	560.3	1060	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PB750R3-632AXSP04	405.6	624.5	480.9	538.4	1031.9	406.1	622.5	480.1	537.4	1025.7	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD15S6PK370C2-425AXSP04	341.4	528.3	405.3	454.4	-	341	524.9	403.4	452.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C2-432AXSP04	315.7	492	375.8	423	-	315.1	489.2	374.4	420.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C2-525AXSP04	380.1	580.5	448.1	500.9	-	379.3	576.8	446.6	498.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C2-532AXSP04	356.7	549.6	422.8	473.3	910.1	355.4	545.8	420.6	470.8	901.2	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C2-625AXSP04	407.1	615.3	478.3	532.4	999.7	406	611.4	475.8	529.5	991	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C2-632AXSP04	387.2	591	456.9	510.5	968.5	386.2	587.1	454.6	507.8	959.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C4-425AXSP04	341.4	528.3	405.3	454.4	-	341	524.9	403.4	452.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C4-432AXSP04	315.7	492	375.8	423	-	315.1	489.2	374.4	420.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C4-525AXSP04	380.1	580.5	448.1	500.9	-	379.3	576.8	446.6	498.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C4-532AXSP04	356.7	549.6	422.8	473.3	910.1	355.4	545.8	420.6	470.8	901.2	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C4-625AXSP04	407.1	615.3	478.3	532.4	999.7	406	611.4	475.8	529.5	991	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C4-632AXSP04	387.2	591	456.9	510.5	968.5	386.2	587.1	454.6	507.8	959.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C5-425AXSP04	341.4	528.3	405.3	454.4	-	341	524.9	403.4	452.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C5-432AXSP04	315.7	492	375.8	423	-	315.1	489.2	374.4	420.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C5-525AXSP04	380.1	580.5	448.1	500.9	-	379.3	576.8	446.6	498.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C5-532AXSP04	356.7	549.6	422.8	473.3	910.1	355.4	545.8	420.6	470.8	901.2	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C5-625AXSP04	407.1	615.3	478.3	532.4	999.7	406	611.4	475.8	529.5	991	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C5-632AXSP04	387.2	591	456.9	510.5	968.5	386.2	587.1	454.6	507.8	959.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C8-425AXSP04	341.4	528.3	405.3	454.4	-	341	524.9	403.4	452.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C8-432AXSP04	315.7	492	375.8	423	-	315.1	489.2	374.4	420.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370C8-525AXSP04	380.1	580.5	448.1	500.9	-	379.3	576.8	446.6	498.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C8-532AXSP04	356.7	549.6	422.8	473.3	910.1	355.4	545.8	420.6	470.8	901.2	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370C8-625AXSP04	407.1	615.3	478.3	532.4	999.7	406	611.4	475.8	529.5	991	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370C8-632AXSP04	387.2	591	456.9	510.5	968.5	386.2	587.1	454.6	507.8	959.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370K2-425AXSP04	329.1	508.2	390.4	437.6	-	328.1	504.9	388.6	435.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370K2-432AXSP04	304.5	473.7	363.1	407.6	-	303.9	470.9	360.9	405.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370K2-525AXSP04	365.6	557.5	430.9	481.5	914	364.7	553.8	428.6	478.9	905.6	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370K2-532AXSP04	343.2	528.6	406.6	455.6	873.1	342.4	524.9	404.4	452.4	865.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370K2-625AXSP04	390.7	589.9	458.9	510.6	956.6	389.5	585.9	456.4	507.8	948	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370K2-632AXSP04	372.1	567.8	438.9	490.2	928.5	371	563.9	437.1	487.4	919.8	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK370K4-425AXSP04	329.1	508.2	390.4	437.6	-	328.1	504.9	388.6	435.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370K4-432AXSP04	304.5	473.7	363.1	407.6	-	303.9	470.9	360.9	405.8	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK370K4-525AXSP04	365.6	557.5	430.9	481.5	914	364.7	553.8	428.6	478.9	905.6	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370K4-532AXSP04	343.2	528.6	406.6	455.6	873.1	342.4	524.9	404.4	452.4	865.7	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK370K4-625AXSP04	390.7	589.9	458.9	510.6	956.6	389.5	585.9	456.4	507.8	948	676	20.6	4"	541	13.6	4"	812	29	4"

EAW-VD15S6PK400R3-425AXSP04	334.8	517.4	397.3	445.3	-	334.4	514.3	395.6	443.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK400R3-432AXSP04	310.4	483.2	369.4	414.9	-	309.8	479.8	368.1	413.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK400R3-525AXSP04	372	567.6	438.5	490.1	930.9	371.3	563.4	436.4	487	922.8	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK400R3-532AXSP04	349.6	538	414.2	463.6	890.5	348.4	534.6	412.2	461.2	882.1	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK400R3-625AXSP04	397.8	600.7	466.6	519.9	974.4	396.7	596.2	464.2	516.6	966.1	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK400R3-632AXSP04	378.5	578	446.6	498.9	945.5	377.6	573.5	445	496.2	937	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK5083-425AXSP04	363.6	563.6	432	484.8	-	363.1	560.9	430.7	483.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK5083-432AXSP04	336.2	525.2	400.7	450.6	-	336.1	522	399.8	449.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK5083-525AXSP04	404	618.5	477.2	533.1	-	403.8	614.6	475.6	531.2	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK5083-532AXSP04	379.4	585.3	450	504.2	-	378.8	582.6	448.6	502.5	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK5083-625AXSP04	431.9	653.9	507.5	565.2	1064.7	431.7	650.3	503.3	563.5	1056.4	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK5083-632AXSP04	411.3	629.1	486.3	542.9	1033.8	410.8	625.8	484.4	540.7	1025.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C2-425AXSP04	380.9	592.1	453.6	509.6	-	380.9	588.9	452	506.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C2-432AXSP04	351.3	548.5	419.2	471.8	-	350.7	546	417.2	469.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C2-525AXSP04	426.5	654.4	504	564.3	-	426	649.9	502	561	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C2-532AXSP04	398.2	616	472.7	530	-	397.9	612.4	470.7	527.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C2-625AXSP04	459.6	696.3	539.5	602	-	458.8	692.5	537.3	599.4	1127.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C2-632AXSP04	434.6	665.4	513.4	574.4	1094.9	434	661.5	511.2	571.7	1086.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C3-425AXSP04	380.9	592.1	453.6	509.6	-	380.9	588.9	452	506.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C3-432AXSP04	351.3	548.5	419.2	471.8	-	350.7	546	417.2	469.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C3-525AXSP04	426.5	654.4	504	564.3	-	426	649.9	502	561	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C3-532AXSP04	398.2	616	472.7	530	-	397.9	612.4	470.7	527.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C3-625AXSP04	459.6	696.3	539.5	602	-	458.8	692.5	537.3	599.4	1127.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C3-632AXSP04	434.6	665.4	513.4	574.4	1094.9	434	661.5	511.2	571.7	1086.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C4-425AXSP04	380.9	592.1	453.6	509.6	-	380.9	588.9	452	506.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C4-432AXSP04	351.3	548.5	419.2	471.8	-	350.7	546	417.2	469.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C4-525AXSP04	426.5	654.4	504	564.3	-	426	649.9	502	561	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C4-532AXSP04	398.2	616	472.7	530	-	397.9	612.4	470.7	527.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C4-625AXSP04	459.6	696.3	539.5	602	-	458.8	692.5	537.3	599.4	1127.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C4-632AXSP04	434.6	665.4	513.4	574.4	1094.9	434	661.5	511.2	571.7	1086.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C5-425AXSP04	380.9	592.1	453.6	509.6	-	380.9	588.9	452	506.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C5-432AXSP04	351.3	548.5	419.2	471.8	-	350.7	546	417.2	469.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C5-525AXSP04	426.5	654.4	504	564.3	-	426	649.9	502	561	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C5-532AXSP04	398.2	616	472.7	530	-	397.9	612.4	470.7	527.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C5-625AXSP04	459.6	696.3	539.5	602	-	458.8	692.5	537.3	599.4	1127.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C5-632AXSP04	434.6	665.4	513.4	574.4	1094.9	434	661.5	511.2	571.7	1086.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C8-425AXSP04	380.9	592.1	453.6	509.6	-	380.9	588.9	452	506.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C8-432AXSP04	351.3	548.5	419.2	471.8	-	350.7	546	417.2	469.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C8-525AXSP04	426.5	654.4	504	564.3	-	426	649.9	502	561	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C8-532AXSP04	398.2	616	472.7	530	-	397.9	612.4	470.7	527.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C8-625AXSP04	459.6	696.3	539.5	602	-	458.8	692.5	537.3	599.4	1127.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C8-632AXSP04	434.6	665.4	513.4	574.4	1094.9	434	661.5	511.2	571.7	1086.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C9-425AXSP04	380.9	592.1	453.6	509.6	-	380.9	588.9	452	506.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C9-432AXSP04	351.3	548.5	419.2	471.8	-	350.7	546	417.2	469.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550C9-525AXSP04	426.5	654.4	504	564.3	-	426	649.9	502	561	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C9-532AXSP04	398.2	616	472.7	530	-	397.9	612.4	470.7	527.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550C9-625AXSP04	459.6	696.3	539.5	602	-	458.8	692.5	537.3	599.4	1127.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550C9-632AXSP04	434.6	665.4	513.4	574.4	1094.9	434	661.5	511.2	571.7	1086.9	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550K2-425AXSP04	365.1	565.9	433.7	486.8	-	364.4	563	432.2	485	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550K2-432AXSP04	337.1	526.5	402.4	452.6	-	336.8	523.2	400.6	450.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550K2-525AXSP04	406.3	622.2	480	537	-	405.9	618.9	478.2	534.1	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550K2-532AXSP04	381.3	588.4	452.3	506.8	-	380.3	585.1	450.5	504.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550K2-625AXSP04	436.3	660.7	512	571	1075.9	435.5	656.2	509.8	568.5	1066.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550K2-632AXSP04	414.2	632.9	489.1	546.8	1040.2	413.6	629.3	487	543.7	1031.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550K3-425AXSP04	365.1	565.9	433.7	486.8	-	364.4	563	432.2	485	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550K3-432AXSP04	337.1	526.5	402.4	452.6	-	336.8	523.2	400.6	450.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550K3-525AXSP04	406.3	622.2	480	537	-	405.9	618.9	478.2	534.1	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550K3-532AXSP04	381.3	588.4	452.3	506.8	-	380.3	585.1	450.5	504.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550K3-625AXSP04	436.3	660.7	512	571	1075.9	435.5	656.2	509.8	568.5	1066.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550K3-632AXSP04	414.2	632.9	489.1	546.8	1040.2	413.6	629.3	487	543.7	1031.6	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD15S6PK550K4-425AXSP04	365.1	565.9	433.7	486.8	-	364.4	563	432.2	485	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550K4-432AXSP04	337.1	526.5	402.4	452.6	-	336.8	523.2	400.6	450.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD15S6PK550K4-525AXSP04	406.3	622.2	480	537	-	405.9	618.9	478.2	534.1	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550K4-532AXSP04	381.3	588.4	452.3	506.8	-	380.3	585.1	450.5	504.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD15S6PK550K4-625AXSP04	436.3	660.7	512	571	1075.9	435.5	656.2	509.8	568.5	1066.2	676	20							

EAW-VD1556PK750C3-632AXSP04	460.6	706.9	544.4	609.4	-	460.7	702.9	542.9	607.7	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C4-425AXSP02	360.4	591.5	442	503.2	1011.7	365.1	592	444.3	504.7	1008	902	10.2	2 (2) 4"	721	9	4"	1082	14.3	2 (2) 4"
EAW-VD1556PK750C4-432AXSP02	373.3	584.4	445.8	501.6	-	373.3	582.5	444.9	499.9	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750C4-525AXSP04	452.5	695.2	535.1	599.5	-	452.1	692.4	533.9	597	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C4-532AXSP04	422.6	655.8	502.8	564.3	-	423	652.1	500.8	561.9	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C4-625AXSP04	486.2	739	571.8	638.3	-	485.7	735.3	570.5	636	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C4-632AXSP04	460.6	706.9	544.4	609.4	-	460.7	702.9	542.9	607.7	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C5-425AXSP02	360.4	591.5	442	503.2	1011.7	365.1	592	444.3	504.7	1008	902	10.2	2 (2) 4"	721	9	4"	1082	14.3	2 (2) 4"
EAW-VD1556PK750C5-432AXSP04	373.3	584.4	445.8	501.6	-	373.3	582.5	444.9	499.9	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750C5-525AXSP04	452.5	695.2	535.1	599.5	-	452.1	692.4	533.9	597	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C5-532AXSP04	422.6	655.8	502.8	564.3	-	423	652.1	500.8	561.9	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C5-625AXSP04	486.2	739	571.8	638.3	-	485.7	735.3	570.5	636	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C5-632AXSP04	460.6	706.9	544.4	609.4	-	460.7	702.9	542.9	607.7	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C8-425AXSP02	360.4	591.5	442	503.2	1011.7	365.1	592	444.3	504.7	1008	902	10.2	2 (2) 4"	721	9	4"	1082	14.3	2 (2) 4"
EAW-VD1556PK750C8-432AXSP04	373.3	584.4	445.8	501.6	-	373.3	582.5	444.9	499.9	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750C8-525AXSP04	452.5	695.2	535.1	599.5	-	452.1	692.4	533.9	597	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C8-532AXSP04	422.6	655.8	502.8	564.3	-	423	652.1	500.8	561.9	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C8-625AXSP04	486.2	739	571.8	638.3	-	485.7	735.3	570.5	636	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C8-632AXSP04	460.6	706.9	544.4	609.4	-	460.7	702.9	542.9	607.7	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C9-425AXSP02	360.4	591.5	442	503.2	1011.7	365.1	592	444.3	504.7	1008	902	10.2	2 (2) 4"	721	9	4"	1082	14.3	2 (2) 4"
EAW-VD1556PK750C9-432AXSP04	373.3	584.4	445.8	501.6	-	373.3	582.5	444.9	499.9	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750C9-525AXSP04	452.5	695.2	535.1	599.5	-	452.1	692.4	533.9	597	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C9-532AXSP04	422.6	655.8	502.8	564.3	-	423	652.1	500.8	561.9	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750C9-625AXSP04	486.2	739	571.8	638.3	-	485.7	735.3	570.5	636	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750C9-632AXSP04	460.6	706.9	544.4	609.4	-	460.7	702.9	542.9	607.7	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K2-425AXSP04	392.1	609.4	466.3	524	-	392.1	607.2	465.5	522.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K2-432AXSP04	361.7	566.1	432.2	486.4	-	361.7	563.2	430.5	484.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K2-525AXSP04	436.7	669.9	516.3	578.2	-	436.3	667.2	515	575.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K2-532AXSP04	409	633.5	485.5	544.6	-	408.8	630.1	484.6	543.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K2-625AXSP04	469.1	711.2	551.6	614.7	-	468.3	708.2	549.2	612.8	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K2-632AXSP04	444.7	681.5	525.5	588	1123.7	444.8	678.6	524	585.4	1115.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K3-425AXSP04	392.1	609.4	466.3	524	-	392.1	607.2	465.5	522.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K3-432AXSP04	361.7	566.1	432.2	486.4	-	361.7	563.2	430.5	484.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K3-525AXSP04	436.7	669.9	516.3	578.2	-	436.3	667.2	515	575.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K3-532AXSP04	409	633.5	485.5	544.6	-	408.8	630.1	484.6	543.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K3-625AXSP04	469.1	711.2	551.6	614.7	-	468.3	708.2	549.2	612.8	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K3-632AXSP04	444.7	681.5	525.5	588	1123.7	444.8	678.6	524	585.4	1115.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K4-425AXSP04	392.1	609.4	466.3	524	-	392.1	607.2	465.5	522.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K4-432AXSP04	361.7	566.1	432.2	486.4	-	361.7	563.2	430.5	484.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K4-525AXSP04	436.7	669.9	516.3	578.2	-	436.3	667.2	515	575.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K4-532AXSP04	409	633.5	485.5	544.6	-	408.8	630.1	484.6	543.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K4-625AXSP04	469.1	711.2	551.6	614.7	-	468.3	708.2	549.2	612.8	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K4-632AXSP04	444.7	681.5	525.5	588	1123.7	444.8	678.6	524	585.4	1115.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K5-425AXSP04	392.1	609.4	466.3	524	-	392.1	607.2	465.5	522.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K5-432AXSP04	361.7	566.1	432.2	486.4	-	361.7	563.2	430.5	484.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K5-525AXSP04	436.7	669.9	516.3	578.2	-	436.3	667.2	515	575.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K5-532AXSP04	409	633.5	485.5	544.6	-	408.8	630.1	484.6	543.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K5-625AXSP04	469.1	711.2	551.6	614.7	-	468.3	708.2	549.2	612.8	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K5-632AXSP04	444.7	681.5	525.5	588	1123.7	444.8	678.6	524	585.4	1115.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K8-425AXSP04	392.1	609.4	466.3	524	-	392.1	607.2	465.5	522.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K8-432AXSP04	361.7	566.1	432.2	486.4	-	361.7	563.2	430.5	484.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K8-525AXSP04	436.7	669.9	516.3	578.2	-	436.3	667.2	515	575.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K8-532AXSP04	409	633.5	485.5	544.6	-	408.8	630.1	484.6	543.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K8-625AXSP04	469.1	711.2	551.6	614.7	-	468.3	708.2	549.2	612.8	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K8-632AXSP04	444.7	681.5	525.5	588	1123.7	444.8	678.6	524	585.4	1115.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K9-425AXSP04	392.1	609.4	466.3	524	-	392.1	607.2	465.5	522.1	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K9-432AXSP04	361.7	566.1	432.2	486.4	-	361.7	563.2	430.5	484.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750K9-525AXSP04	436.7	669.9	516.3	578.2	-	436.3	667.2	515	575.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K9-532AXSP04	409	633.5	485.5	544.6	-	408.8	630.1	484.6	543.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750K9-625AXSP04	469.1	711.2	551.6	614.7	-	468.3	708.2	549.2	612.8	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750K9-632AXSP04	444.7	681.5	525.5	588	1123.7	444.8	678.6	524	585.4	1115.7	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD1556PK750R3-425AXSP04	384.2	596.3	456.7	513.1	-	383.6	594.3	455.2	511.2	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750R3-432AXSP04	354.9	555.1	423.2	476.4	-	354.5	552.2	422.6	474.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD1556PK750R3-525AXSP04	427.3	654.7	505	564.5	-	426.7	652	502.9	562.9	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750R3-532AXSP04	400.6	619.9	475.5	533.2	-	400.4	616.5	474.5	531	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD1556PK750R3-625AXSP04	458.5	694.5	538.2	600.5	-	457.6	690.6	536.6	597.										

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6ZB370K4-625AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB370K4-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB370K5-425AXSP04	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB370K5-432AXSP04	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB370K5-525AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB370K5-532AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB370K5-625AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB370K5-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB370K8-425AXSP04	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB370K8-432AXSP04	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB370K8-525AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB370K8-532AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB370K8-625AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB370K8-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400B3-425AXSP04	361	559	429.4	481.4	926.9	359.8	554.4	426.6	478.2	917.9	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400B3-432AXSP04	333.8	521.5	399	448.1	870.3	333.1	517.5	397.4	445.4	863.2	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400B3-525AXSP06	414.7	624.9	485.4	540.9	-	412	619.3	481.8	536.1	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400B3-532AXSP04	374.4	578.7	444.7	498.8	956.5	373.6	574.5	442.4	495.9	946.9	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB400B3-625AXSP06	444.3	661.3	516.7	573.6	-	440.9	654.2	512.3	568.8	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400B3-632AXSP06	423.3	636.7	495.4	551	-	420.4	630.1	490.8	546.6	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400C3-425AXSP04	369.9	572.5	440	493.5	951.4	369.1	568.4	437.6	489.9	941.6	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400C3-432AXSP04	341.3	532.9	408.1	458.5	891.4	340.4	529.5	405.5	455.5	882.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400C3-525AXSP04	409.9	627.9	485.1	542.6	1031.1	408.6	623.2	482.2	538.6	1019.4	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB400C3-532AXSP06	400	608.3	470.4	525.6	-	397.3	602.6	466.7	520.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400C3-632AXSP06	458	682.2	532.7	592.3	-	454.7	675.2	528.5	586.1	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400C3-632AXSP06	435.1	654.9	509.2	566.5	-	432	648	504.4	561.1	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400C9-425AXSP04	369.9	572.5	440	493.5	951.4	369.1	568.4	437.6	489.9	941.6	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400C9-432AXSP04	341.3	532.9	408.1	458.5	891.4	340.4	529.5	405.5	455.5	882.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400C9-525AXSP04	409.9	627.9	485.1	542.6	1031.1	408.6	623.2	482.2	538.6	1019.4	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB400C9-532AXSP06	400	608.3	470.4	525.6	-	397.3	602.6	466.7	520.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400C9-625AXSP06	458	682.2	532.7	592.3	-	454.7	675.2	528.5	586.1	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400C9-632AXSP06	435.1	654.9	509.2	566.5	-	432	648	504.4	561.1	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K3-425AXSP04	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K3-432AXSP04	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K3-525AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K3-532AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K3-625AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K3-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-425AXSP04	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-432AXSP04	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-525AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-532AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-625AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-632AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-632AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-632AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-632AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	329.4	514.1	393.6	442.7	858.9	328.6	510.9	391.9	439.9	850.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	409.1	616.2	479.6	533.6	-	406.4	610.6	475.2	528.7	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-632AXSP06	384.7	585.1	452.3	505.2	-	382.3	579	448.9	500.6	-	507	29.2	3"	406	19.2	3"	609	36.5	4"
EAW-VD15S6ZB400K9-632AXSP06	438.9	653.1	510.4	566.6	-	435.7	646.4	506.3	561.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	417.7	628	488.7	543.5	-	414.7	621.3	484.1	539.1	1005.9	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB400K9-632AXSP06	356.2	551.1	423.5	474.8	913.6	355.5	546.6	421.4	471.5	904.5	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB400K9-632AXSP06	329.4	514.1	393.6	442.7	858.9														

EAW-VD15S6ZB550K3-532AXSP04	413	640	491	550.5	1061	411.8	635.2	488.9	547.9	1049.8	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K3-625AXSP06	493.1	736.7	574.4	638.9	-	490.1	729.8	570.4	633.6	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K3-632AXSP06	467.8	705.8	548.5	610.5	-	465	699	543.9	605.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K4-425AXSP04	398.2	617.4	473.3	531.4	-	397.3	613	470.7	528.3	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K4-432AXSP04	367.5	574.2	439.1	493	961.8	366.5	570.4	437	490.5	953.4	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K4-525AXSP04	441.8	677.6	522.4	584.8	1114.5	440.2	672.3	519.8	581	1102.9	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K4-532AXSP04	413	640	491	550.5	1061	411.8	635.2	488.9	547.9	1049.8	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K4-625AXSP06	493.1	736.7	574.4	638.9	-	490.1	729.8	570.4	633.6	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K4-632AXSP06	467.8	705.8	548.5	610.5	-	465	699	543.9	605.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K5-425AXSP04	398.2	617.4	473.3	531.4	-	397.3	613	470.7	528.3	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K5-432AXSP04	367.5	574.2	439.1	493	961.8	366.5	570.4	437	490.5	953.4	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K5-525AXSP04	441.8	677.6	522.4	584.8	1114.5	440.2	672.3	519.8	581	1102.9	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K5-532AXSP04	413	640	491	550.5	1061	411.8	635.2	488.9	547.9	1049.8	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K5-625AXSP06	493.1	736.7	574.4	638.9	-	490.1	729.8	570.4	633.6	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K5-632AXSP06	467.8	705.8	548.5	610.5	-	465	699	543.9	605.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K8-425AXSP04	398.2	617.4	473.3	531.4	-	397.3	613	470.7	528.3	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K8-432AXSP04	367.5	574.2	439.1	493	961.8	366.5	570.4	437	490.5	953.4	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K8-525AXSP04	441.8	677.6	522.4	584.8	1114.5	440.2	672.3	519.8	581	1102.9	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K8-532AXSP04	413	640	491	550.5	1061	411.8	635.2	488.9	547.9	1049.8	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K8-625AXSP06	493.1	736.7	574.4	638.9	-	490.1	729.8	570.4	633.6	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K8-632AXSP06	467.8	705.8	548.5	610.5	-	465	699	543.9	605.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K9-425AXSP04	398.2	617.4	473.3	531.4	-	397.3	613	470.7	528.3	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K9-432AXSP04	367.5	574.2	439.1	493	961.8	366.5	570.4	437	490.5	953.4	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550K9-525AXSP04	441.8	677.6	522.4	584.8	1114.5	440.2	672.3	519.8	581	1102.9	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K9-532AXSP04	413	640	491	550.5	1061	411.8	635.2	488.9	547.9	1049.8	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550K9-625AXSP06	493.1	736.7	574.4	638.9	-	490.1	729.8	570.4	633.6	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550K9-632AXSP06	467.8	705.8	548.5	610.5	-	465	699	543.9	605.4	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB550R3-425AXSP04	408.7	634.6	486	545.9	-	408	630.3	484.3	542.9	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550R3-432AXSP04	376.9	589.9	450.6	507.1	989.2	376.8	586.3	448.6	504.7	981	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB550R3-525AXSP04	453.6	696.5	537.3	600.8	1146.4	452.9	691.3	534.9	597.1	1136.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550R3-532AXSP04	423.8	657.8	505	566.3	1091.3	423.5	653	503	563	1081.6	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB550R3-625AXSP06	489.3	743.9	576.4	643.4	1210.2	488.3	738.6	573.9	639.6	1198.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB550R3-632AXSP06	480.3	726.4	563.3	628.1	-	477.7	719.6	559.6	623	-	609	26.7	4"	487	20.5	3"	730	37.4	4"
EAW-VD15S6ZB750C2-425AXSP04	444.5	691.2	529.2	594.2	-	444.1	686.9	526.9	591.4	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C2-432AXSP04	409.4	640.8	488.4	550.5	-	408.9	637.1	487.5	548.2	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C2-525AXSP04	495.8	761.8	586.9	657	1258.5	494.9	756.9	584	653.6	1248.5	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C2-532AXSP04	461.9	716.5	550	616.6	1192.2	461.2	712.9	547.3	613.4	1182.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C2-625AXSP04	535.5	815.4	632.1	705.2	1332	534.7	809.9	628.7	701.3	1319.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C2-632AXSP04	505.7	778.4	600.1	671.2	1281.8	505.3	773.1	597.8	668.4	1271.3	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C3-425AXSP04	444.5	691.2	529.2	594.2	-	444.1	686.9	526.9	591.4	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C3-432AXSP04	409.4	640.8	488.4	550.5	-	408.9	637.1	487.5	548.2	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C3-525AXSP04	495.8	761.8	586.9	657	1258.5	494.9	756.9	584	653.6	1248.5	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C3-532AXSP04	461.9	716.5	550	616.6	1192.2	461.2	712.9	547.3	613.4	1182.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C3-625AXSP04	535.5	815.4	632.1	705.2	1332	534.7	809.9	628.7	701.3	1319.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C3-632AXSP04	505.7	778.4	600.1	671.2	1281.8	505.3	773.1	597.8	668.4	1271.3	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C4-425AXSP04	444.5	691.2	529.2	594.2	-	444.1	686.9	526.9	591.4	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C4-432AXSP04	409.4	640.8	488.4	550.5	-	408.9	637.1	487.5	548.2	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C4-525AXSP04	495.8	761.8	586.9	657	1258.5	494.9	756.9	584	653.6	1248.5	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C4-532AXSP04	461.9	716.5	550	616.6	1192.2	461.2	712.9	547.3	613.4	1182.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C4-625AXSP04	535.5	815.4	632.1	705.2	1332	534.7	809.9	628.7	701.3	1319.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C4-632AXSP04	505.7	778.4	600.1	671.2	1281.8	505.3	773.1	597.8	668.4	1271.3	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C5-425AXSP04	444.5	691.2	529.2	594.2	-	444.1	686.9	526.9	591.4	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C5-432AXSP04	409.4	640.8	488.4	550.5	-	408.9	637.1	487.5	548.2	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C5-525AXSP04	495.8	761.8	586.9	657	1258.5	494.9	756.9	584	653.6	1248.5	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C5-532AXSP04	461.9	716.5	550	616.6	1192.2	461.2	712.9	547.3	613.4	1182.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C5-625AXSP04	535.5	815.4	632.1	705.2	1332	534.7	809.9	628.7	701.3	1319.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C5-632AXSP04	505.7	778.4	600.1	671.2	1281.8	505.3	773.1	597.8	668.4	1271.3	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C8-425AXSP04	444.5	691.2	529.2	594.2	-	444.1	686.9	526.9	591.4	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C8-432AXSP04	409.4	640.8	488.4	550.5	-	408.9	637.1	487.5	548.2	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750C8-525AXSP04	495.8	761.8	586.9	657	1258.5	494.9	756.9	584	653.6	1248.5	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C8-532AXSP04	461.9	716.5	550	616.6	1192.2	461.2	712.9	547.3	613.4	1182.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750C8-625AXSP04	535.5	815.4	632.1	705.2	1332	534.7	809.9	628.7	701.3	1319.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750C8-632AXSP04	505.7	778.4	600.1	671.2	1281.8	505.3	773.1	597.8	668.4	1271.3	913	17.5	(2) 4"	730	14	4"	1096	24.6	

EAW-VD15S6ZB750K9-525AXSP04	478.3	734.9	565.9	634.2	1212.7	477.1	729.9	563.8	630.7	1201.2	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750K9-532AXSP04	446.4	692.5	531.4	596.4	1150.9	445.7	688	529.7	593.3	1141.4	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750K9-532AXSP04	516.1	784.8	608.2	678.3	1279.5	515.5	779.9	606	674.8	1268.5	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750K9-632AXSP04	488.7	751	578.8	648.1	1235.7	488.1	745.7	576.4	644.3	1223.6	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750R3-425AXSP04	421.4	654.4	501.3	562.5	-	421	650.4	499.2	559.8	-	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750R3-432AXSP04	388.7	608.4	464	522.5	-	388.1	605.1	463.2	520.4	1013.6	609	18.5	4"	487	15.1	3"	730	26	4"
EAW-VD15S6ZB750R3-525AXSP04	467.4	718.5	553.7	619.4	1183.4	466.9	713.6	550.8	616	1173.7	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750R3-532AXSP04	436.9	678	519.9	583.3	1126	436.2	673.5	518.2	580.3	1116.6	755	19.7	4"	604	13	4"	906	24	(2) 4"
EAW-VD15S6ZB750R3-625AXSP04	503.6	766.2	593.3	662.5	1247.1	503	760.4	591.2	659.1	1236.4	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZB750R3-632AXSP04	477.7	734.4	565.6	633.1	1206.1	477	729.2	563.2	630.3	1195.8	913	17.5	(2) 4"	730	14	4"	1096	24.6	(2) 4"
EAW-VD15S6ZK017G7-425AXSP02	495.7	814.1	608.3	693.5	1391.6	500.9	813.4	609.9	693.1	1383.9	1217	11.2	(2) 4"	974	7.4	(2) 4"	1461	15.7	(2) 4"
EAW-VD15S6ZK017G7-432AXSP04	509.3	797	608.3	685.3	-	507.8	792.2	605.2	680.9	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK017G7-525AXSP04	628.5	967.7	744.8	833.7	-	626.5	961.5	740.2	828.2	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK017G7-532AXSP04	581.4	902.4	690.9	775.8	-	579	895.5	686.9	771	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK017G7-625AXSP04	688.7	1048.7	811.3	906.3	-	686.7	1040	805.8	899.9	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK017G7-632AXSP04	644.1	990.1	761.5	853	-	641.8	982	757.7	847.2	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK370C2-425AXSP04	390.1	599.6	462.1	516.9	991.5	388.1	594.7	458.4	512.7	980.5	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C2-432AXSP04	359.9	558.5	428.2	480.6	930.4	358.5	554.3	425.8	476.9	920.2	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C2-525AXSP04	432.6	658	510.1	568.6	1074.8	430.5	652.1	505.6	564.3	1062.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C2-532AXSP04	404.7	622	479.6	536.7	1024.1	402.4	615.8	475.6	532	1012.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C2-625AXSP04	466.2	701.5	546.4	608.3	1132.9	463.7	694.5	541.7	602.9	1119.3	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK370C2-632AXSP06	456.7	684.3	532.9	593.3	-	452.8	676.1	527.9	586.9	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370C4-425AXSP04	390.1	599.6	462.1	516.9	991.5	388.1	594.7	458.4	512.7	980.5	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C4-432AXSP04	359.9	558.5	428.2	480.6	930.4	358.5	554.3	425.8	476.9	920.2	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C4-525AXSP04	432.6	658	510.1	568.6	1074.8	430.5	652.1	505.6	564.3	1062.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C4-532AXSP04	404.7	622	479.6	536.7	1024.1	402.4	615.8	475.6	532	1012.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C4-625AXSP04	466.2	701.5	546.4	608.3	1132.9	463.7	694.5	541.7	602.9	1119.3	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK370C4-632AXSP06	456.7	684.3	532.9	593.3	-	452.8	676.1	527.9	586.9	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370C5-425AXSP04	390.1	599.6	462.1	516.9	991.5	388.1	594.7	458.4	512.7	980.5	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C5-432AXSP04	359.9	558.5	428.2	480.6	930.4	358.5	554.3	425.8	476.9	920.2	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C5-525AXSP04	432.6	658	510.1	568.6	1074.8	430.5	652.1	505.6	564.3	1062.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C5-532AXSP04	404.7	622	479.6	536.7	1024.1	402.4	615.8	475.6	532	1012.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C8-425AXSP04	390.1	599.6	462.1	516.9	991.5	388.1	594.7	458.4	512.7	980.5	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C8-432AXSP04	359.9	558.5	428.2	480.6	930.4	358.5	554.3	425.8	476.9	920.2	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370C8-525AXSP04	432.6	658	510.1	568.6	1074.8	430.5	652.1	505.6	564.3	1062.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C8-532AXSP04	404.7	622	479.6	536.7	1024.1	402.4	615.8	475.6	532	1012.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370C8-625AXSP04	466.2	701.5	546.4	608.3	1132.9	463.7	694.5	541.7	602.9	1119.3	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK370C8-632AXSP06	456.7	684.3	532.9	593.3	-	452.8	676.1	527.9	586.9	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K2-425AXSP04	375.6	577.3	444.7	498.1	953.7	374.4	572.8	442	494.1	943.4	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K2-432AXSP04	347.7	539.5	414.2	464.6	897.6	346.3	534.6	411.2	461.1	887.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K2-525AXSP04	415.5	631.1	489.1	545.7	1030	413.6	625.7	485.6	541.8	1017.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K2-532AXSP04	389.5	598.6	461.4	516.1	984.7	388	592.8	458.3	512.5	972.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K2-625AXSP06	460.7	682.8	535	592.9	-	456.9	674.4	529.5	586.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K2-632AXSP06	438.6	656.4	511.7	568.7	-	435	648.8	507	562.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K4-425AXSP04	375.6	577.3	444.7	498.1	953.7	374.4	572.8	442	494.1	943.4	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K4-432AXSP04	347.7	539.5	414.2	464.6	897.6	346.3	534.6	411.2	461.1	887.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K4-525AXSP04	415.5	631.1	489.1	545.7	1030	413.6	625.7	485.6	541.8	1017.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K4-532AXSP04	389.5	598.6	461.4	516.1	984.7	388	592.8	458.3	512.5	972.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K4-625AXSP06	460.7	682.8	535	592.9	-	456.9	674.4	529.5	586.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K4-632AXSP06	438.6	656.4	511.7	568.7	-	435	648.8	507	562.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K5-425AXSP04	375.6	577.3	444.7	498.1	953.7	374.4	572.8	442	494.1	943.4	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K5-432AXSP04	347.7	539.5	414.2	464.6	897.6	346.3	534.6	411.2	461.1	887.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K5-525AXSP04	415.5	631.1	489.1	545.7	1030	413.6	625.7	485.6	541.8	1017.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K5-532AXSP04	389.5	598.6	461.4	516.1	984.7	388	592.8	458.3	512.5	972.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K5-625AXSP06	460.7	682.8	535	592.9	-	456.9	674.4	529.5	586.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K5-632AXSP06	438.6	656.4	511.7	568.7	-	435	648.8	507	562.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K8-425AXSP04	375.6	577.3	444.7	498.1	953.7	374.4	572.8	442	494.1	943.4	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K8-432AXSP04	347.7	539.5	414.2	464.6	897.6	346.3	534.6	411.2	461.1	887.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK370K8-525AXSP04	415.5	631.1	489.1	545.7	1030	413.6	625.7	485.6	541.8	1017.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K8-532AXSP04	389.5	598.6	461.4	516.1	984.7	388	592.8	458.3	512.5	972.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK370K8-625AXSP06	460.7	682.8	535	592.9	-	456.9	674.4	529.5	586.8	-	609	29.2	4"	487	22.2	3"	730	41	4"
EAW-VD15S6ZK370K8-632AXSP06	438.6	656.4	511.7	568.7	-	435	648.8	507	562.8	-	609	29.2	4"	487	22.2	3"	730		

EAW-VD15S6ZK550B3-432AXSP04	387.9	602.3	461.2	518.2	1004.6	386.3	597.6	458.5	514.9	994.7	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550B3-525AXSP04	465.7	710.1	549.5	613.7	1163.1	464.2	704	545.5	609.2	1150.1	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550B3-532AXSP04	436.2	670.5	516.5	578.5	1107.6	434.3	665.5	513.6	574.2	1096.2	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550B3-625AXSP04	502.1	757	588.8	655.8	1225.2	499.5	750.4	585.1	650.8	1211.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550B3-632AXSP04	476.3	725.5	561.6	627.7	1185.1	474.5	719	558.1	622.8	1172.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C2-425AXSP04	437.9	675.8	519.4	582	-	436.2	670.9	515.8	578.7	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C2-432AXSP04	403.3	627.6	479.8	539.4	-	402.1	622.3	477.4	535.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C2-525AXSP04	488.6	745.3	576.7	643.6	1223.6	486.7	739.2	572.1	639.2	1210.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C2-532AXSP04	455.4	701.4	539.5	604.6	1160.1	453.3	695.9	536.3	599.9	1147.6	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C2-625AXSP04	529.7	799.7	621.3	692.3	1296.8	526.6	791.2	617.1	686.6	1281.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C2-632AXSP04	499.5	762.2	589.3	659	1247.8	497.4	754.8	585.2	653.4	1232.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C3-425AXSP04	437.9	675.8	519.4	582	-	436.2	670.9	515.8	578.7	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C3-432AXSP04	403.3	627.6	479.8	539.4	-	402.1	622.3	477.4	535.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C3-525AXSP04	488.6	745.3	576.7	643.6	1223.6	486.7	739.2	572.1	639.2	1210.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C3-532AXSP04	455.4	701.4	539.5	604.6	1160.1	453.3	695.9	536.3	599.9	1147.6	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C3-625AXSP04	529.7	799.7	621.3	692.3	1296.8	526.6	791.2	617.1	686.6	1281.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C3-632AXSP04	499.5	762.2	589.3	659	1247.8	497.4	754.8	585.2	653.4	1232.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C4-425AXSP04	437.9	675.8	519.4	582	-	436.2	670.9	515.8	578.7	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C4-432AXSP04	403.3	627.6	479.8	539.4	-	402.1	622.3	477.4	535.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C4-525AXSP04	488.6	745.3	576.7	643.6	1223.6	486.7	739.2	572.1	639.2	1210.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C4-532AXSP04	455.4	701.4	539.5	604.6	1160.1	453.3	695.9	536.3	599.9	1147.6	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C4-625AXSP04	529.7	799.7	621.3	692.3	1296.8	526.6	791.2	617.1	686.6	1281.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C4-632AXSP04	499.5	762.2	589.3	659	1247.8	497.4	754.8	585.2	653.4	1232.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C8-425AXSP04	437.9	675.8	519.4	582	-	436.2	670.9	515.8	578.7	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C8-432AXSP04	403.3	627.6	479.8	539.4	-	402.1	622.3	477.4	535.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C8-525AXSP04	488.6	745.3	576.7	643.6	1223.6	486.7	739.2	572.1	639.2	1210.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C8-532AXSP04	455.4	701.4	539.5	604.6	1160.1	453.3	695.9	536.3	599.9	1147.6	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C8-625AXSP04	529.7	799.7	621.3	692.3	1296.8	526.6	791.2	617.1	686.6	1281.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C8-632AXSP04	499.5	762.2	589.3	659	1247.8	497.4	754.8	585.2	653.4	1232.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550C9-425AXSP04	437.9	675.8	519.4	582	-	436.2	670.9	515.8	578.7	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C9-432AXSP04	403.3	627.6	479.8	539.4	-	402.1	622.3	477.4	535.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550C9-525AXSP04	488.6	745.3	576.7	643.6	1223.6	486.7	739.2	572.1	639.2	1210.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550C9-532AXSP04	455.4	701.4	539.5	604.6	1160.1	453.3	695.9	536.3	599.9	1147.6	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K2-432AXSP04	388.7	603.8	463.1	519.4	1008.6	387.8	599.1	460.3	516.1	998.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K2-525AXSP04	467.3	711.6	550.5	614.9	1165.6	465	705.3	547.2	610.3	1153.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K2-532AXSP04	437	672.8	518.3	579.6	1110	435.2	667	514.6	575.4	1098.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K2-625AXSP04	503.9	759.7	591.6	658.1	1231.1	501.7	752.8	587	652.9	1215.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K2-632AXSP04	477.1	727.9	562.7	629	1189	475.3	721.2	559.1	624	1175.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K3-425AXSP04	420.6	648.9	498.7	558.5	-	419.2	643.5	495.4	555.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K3-432AXSP04	388.7	603.8	463.1	519.4	1008.6	387.8	599.1	460.3	516.1	998.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K3-525AXSP04	467.3	711.6	550.5	614.9	1165.6	465	705.3	547.2	610.3	1153.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K3-532AXSP04	437	672.8	518.3	579.6	1110	435.2	667	514.6	575.4	1098.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K3-625AXSP04	503.9	759.7	591.6	658.1	1231.1	501.7	752.8	587	652.9	1215.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K3-632AXSP04	477.1	727.9	562.7	629	1189	475.3	721.2	559.1	624	1175.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K4-425AXSP04	420.6	648.9	498.7	558.5	-	419.2	643.5	495.4	555.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K4-432AXSP04	388.7	603.8	463.1	519.4	1008.6	387.8	599.1	460.3	516.1	998.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K4-525AXSP04	467.3	711.6	550.5	614.9	1165.6	465	705.3	547.2	610.3	1153.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K4-532AXSP04	437	672.8	518.3	579.6	1110	435.2	667	514.6	575.4	1098.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K4-625AXSP04	503.9	759.7	591.6	658.1	1231.1	501.7	752.8	587	652.9	1215.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K4-632AXSP04	477.1	727.9	562.7	629	1189	475.3	721.2	559.1	624	1175.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K5-425AXSP04	420.6	648.9	498.7	558.5	-	419.2	643.5	495.4	555.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K5-432AXSP04	388.7	603.8	463.1	519.4	1008.6	387.8	599.1	460.3	516.1	998.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K5-525AXSP04	467.3	711.6	550.5	614.9	1165.6	465	705.3	547.2	610.3	1153.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K5-532AXSP04	437	672.8	518.3	579.6	1110	435.2	667	514.6	575.4	1098.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K5-625AXSP04	503.9	759.7	591.6	658.1	1231.1	501.7	752.8	587	652.9	1215.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K5-632AXSP04	477.1	727.9	562.7	629	1189	475.3	721.2	559.1	624	1175.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K8-425AXSP04	420.6	648.9	498.7	558.5	-	419.2	643.5	495.4	555.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K8-432AXSP04	388.7	603.8	463.1	519.4	1008.6	387.8	599.1	460.3	516.1	998.8	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK550K8-525AXSP04	467.3	711.6	550.5	614.9	1165.6	465	705.3	547.2	610.3	1153.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K8-532AXSP04	437	672.8	518.3	579.6	1110	435.2	667	514.6	575.4	1098.7	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK550K8-625AXSP04	503.9	759.7	591.6	658.1	1231.1	501.7	752.8	587	652.9	1215.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK550K8-632AXSP																			

EAW-VD15S6ZK750C5-425AXSP04	470.9	728.2	559.1	627.1	-	468.9	723.8	555.8	623.2	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750C5-432AXSP04	433.4	675.1	516.2	580	-	432.1	670.4	513.6	576.9	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750C5-525AXSP04	525.5	803.7	619.7	693.1	-	523.5	797.3	616.6	688.4	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750C5-532AXSP04	490.4	755.5	580.5	651.2	1252.4	488	749.4	577.7	646.8	1240.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750C5-625AXSP04	569.2	860.1	667.9	744.7	1399.8	566.9	853.3	664.4	739.7	1385.6	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750C5-632AXSP04	537	820.5	634.8	708.4	1347.2	535.6	814.8	630.5	703.5	1332.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750C8-425AXSP04	470.9	728.2	559.1	627.1	-	468.9	723.8	555.8	623.2	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750C8-432AXSP04	433.4	675.1	516.2	580	-	432.1	670.4	513.6	576.9	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750C8-525AXSP04	525.5	803.7	619.7	693.1	-	523.5	797.3	616.6	688.4	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750C8-532AXSP04	490.4	755.5	580.5	651.2	1252.4	488	749.4	577.7	646.8	1240.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750C8-625AXSP04	569.2	860.1	667.9	744.7	1399.8	566.9	853.3	664.4	739.7	1385.6	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750C8-632AXSP04	537	820.5	634.8	708.4	1347.2	535.6	814.8	630.5	703.5	1332.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750C9-425AXSP04	470.9	728.2	559.1	627.1	-	468.9	723.8	555.8	623.2	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750C9-432AXSP04	433.4	675.1	516.2	580	-	432.1	670.4	513.6	576.9	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750C9-525AXSP04	525.5	803.7	619.7	693.1	-	523.5	797.3	616.6	688.4	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750C9-532AXSP04	490.4	755.5	580.5	651.2	1252.4	488	749.4	577.7	646.8	1240.3	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750C9-625AXSP04	569.2	860.1	667.9	744.7	1399.8	566.9	853.3	664.4	739.7	1385.6	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750C9-632AXSP04	537	820.5	634.8	708.4	1347.2	535.6	814.8	630.5	703.5	1332.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K2-425AXSP04	455.7	704.7	540.8	606.3	-	454.7	699.5	537.8	602.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K2-432AXSP04	421.1	654.6	501.2	562.9	-	419.8	650.2	498.8	560	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K2-525AXSP04	507.7	774.3	598.5	669.1	-	505.8	768.2	594.6	664.6	1260.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K2-532AXSP04	474.2	730.5	562	629.2	1209.7	472.8	724.9	558.6	625.2	1198.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K2-625AXSP04	548.2	828.4	643.9	716.8	1345.8	545.7	821.7	639.5	711.8	1331.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K2-632AXSP04	518.9	791.7	612.3	684	1297.1	516.7	785.2	609	679.2	1283.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K3-425AXSP04	455.7	704.7	540.8	606.3	-	454.7	699.5	537.8	602.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K3-432AXSP04	421.1	654.6	501.2	562.9	-	419.8	650.2	498.8	560	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K3-525AXSP04	507.7	774.3	598.5	669.1	-	505.8	768.2	594.6	664.6	1260.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K3-532AXSP04	474.2	730.5	562	629.2	1209.7	472.8	724.9	558.6	625.2	1198.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K3-625AXSP04	548.2	828.4	643.9	716.8	1345.8	545.7	821.7	639.5	711.8	1331.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K3-632AXSP04	518.9	791.7	612.3	684	1297.1	516.7	785.2	609	679.2	1283.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K4-425AXSP04	455.7	704.7	540.8	606.3	-	454.7	699.5	537.8	602.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K4-432AXSP04	421.1	654.6	501.2	562.9	-	419.8	650.2	498.8	560	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K4-525AXSP04	507.7	774.3	598.5	669.1	-	505.8	768.2	594.6	664.6	1260.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K4-532AXSP04	474.2	730.5	562	629.2	1209.7	472.8	724.9	558.6	625.2	1198.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K4-625AXSP04	548.2	828.4	643.9	716.8	1345.8	545.7	821.7	639.5	711.8	1331.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K4-632AXSP04	518.9	791.7	612.3	684	1297.1	516.7	785.2	609	679.2	1283.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K5-425AXSP04	455.7	704.7	540.8	606.3	-	454.7	699.5	537.8	602.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K5-432AXSP04	421.1	654.6	501.2	562.9	-	419.8	650.2	498.8	560	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K5-525AXSP04	507.7	774.3	598.5	669.1	-	505.8	768.2	594.6	664.6	1260.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K5-532AXSP04	474.2	730.5	562	629.2	1209.7	472.8	724.9	558.6	625.2	1198.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K5-625AXSP04	548.2	828.4	643.9	716.8	1345.8	545.7	821.7	639.5	711.8	1331.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K5-632AXSP04	518.9	791.7	612.3	684	1297.1	516.7	785.2	609	679.2	1283.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K8-425AXSP04	455.7	704.7	540.8	606.3	-	454.7	699.5	537.8	602.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K8-432AXSP04	421.1	654.6	501.2	562.9	-	419.8	650.2	498.8	560	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K8-525AXSP04	507.7	774.3	598.5	669.1	-	505.8	768.2	594.6	664.6	1260.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K8-532AXSP04	474.2	730.5	562	629.2	1209.7	472.8	724.9	558.6	625.2	1198.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K8-625AXSP04	548.2	828.4	643.9	716.8	1345.8	545.7	821.7	639.5	711.8	1331.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K8-632AXSP04	518.9	791.7	612.3	684	1297.1	516.7	785.2	609	679.2	1283.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K9-425AXSP04	455.7	704.7	540.8	606.3	-	454.7	699.5	537.8	602.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K9-432AXSP04	421.1	654.6	501.2	562.9	-	419.8	650.2	498.8	560	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750K9-525AXSP04	507.7	774.3	598.5	669.1	-	505.8	768.2	594.6	664.6	1260.5	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K9-532AXSP04	474.2	730.5	562	629.2	1209.7	472.8	724.9	558.6	625.2	1198.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750K9-625AXSP04	548.2	828.4	643.9	716.8	1345.8	545.7	821.7	639.5	711.8	1331.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750K9-632AXSP04	518.9	791.7	612.3	684	1297.1	516.7	785.2	609	679.2	1283.2	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750R3-425AXSP04	446.1	690.1	529.2	594.1	-	445	685.1	527.2	590.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750R3-432AXSP04	412.7	642	491.1	551.4	-	411.5	637.7	488.8	548.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD15S6ZK750R3-525AXSP04	496.2	757.2	584.8	653.6	1243.4	494.3	751.2	581	649.3	1230.4	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750R3-532AXSP04	464.1	714.2	549.9	616.4	1182.1	462.6	709.8	546.5	612.4	1171.1	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD15S6ZK750R3-625AXSP04	535.2	808.2	628.6	699.5	1312.4	533.4	801.6	624.2	694.6	1297.4	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD15S6ZK750R3-632AXSP04	507.2	773.2	598.4	668.3	1266.3	505.1	767.9	595.1	663.7	1254.3	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9102PA177F7-425AXSP16	-	56.1	41.5	47.5	96.9	-	56.3	41.9	47.8	96.7	113	13.8	1-1/2"	90	9.1	1-1/2"	135	19.5	1-1/2"
EAW-VD9102PA177F7-432AXSP16	-	52.2	38.5	44.2	91	-	52.4	38.9	44.4	90.9	113	13.8	1-1/2"	90	9.1</				

EAW-VD9102P3J20P5-632AXSP16	-	80.7	60.4	68.7	137.6	-	80.9	60.8	69	136.9	169	13.9	2"	135	12.2	1-1/2"	203	19.6	2"
EAW-VD9102P3J20P7-425AXSP16	44.2	73.1	54.5	62.1	125.5	44.8	73.3	54.8	62.3	125	113	14.6	1-1/2"	90	9.6	1-1/2"	135	20.5	1-1/2"
EAW-VD9102P3J20P7-432AXSP16	40.4	67.4	50	57.2	116.6	41	67.6	50.4	57.4	116.2	113	14.6	1-1/2"	90	9.6	1-1/2"	135	20.5	1-1/2"
EAW-VD9102P3J20P7-525AXSP16	48.2	79.2	59.2	67.3	134.9	48.9	79.3	59.5	67.6	134.4	135	16	1-1/2"	108	10.5	1-1/2"	162	18.3	2"
EAW-VD9102P3J20P7-532AXSP16	-	73.9	55	62.8	127.2	45.3	74.1	55.4	63	126.7	135	16	1-1/2"	108	10.5	1-1/2"	162	18.3	2"
EAW-VD9102P3J20P7-625AXSP16	-	86.4	64.9	73.7	145.8	-	86.6	65.4	74	145.2	169	13.9	2"	135	12.2	1-1/2"	203	19.6	2"
EAW-VD9102P3J20P7-632AXSP16	-	82.1	61.3	69.8	139.8	-	82.2	61.8	70.2	139.2	169	13.9	2"	135	12.2	1-1/2"	203	19.6	2"
EAW-VD9102ZA177F7-425AXSP16	-	63.8	-	54	110.2	-	63.8	-	54.3	109.6	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA177F7-432AXSP16	-	59.1	-	50	103.1	-	59.2	-	50.3	102.6	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA177F7-525AXSP16	-	69.5	-	-	119.2	-	69.7	-	-	118.4	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA177F7-532AXSP16	-	65.4	-	-	113.3	-	65.7	-	-	112.7	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA177F7-625AXSP16	-	-	-	-	127.3	-	75.3	-	-	126.4	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA177F7-632AXSP16	-	-	-	-	123.2	-	-	-	-	122.4	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA24716-425AXSP16	-	69.6	51.5	58.9	120.4	-	69.8	52	59.2	119.8	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA24716-432AXSP16	-	64.4	-	54.5	112.5	-	64.6	-	54.8	112.1	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA24716-525AXSP16	-	76.1	-	64.6	130.7	-	76.3	-	65	129.9	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA24716-532AXSP16	-	71.5	-	60.6	123.9	-	71.6	-	60.9	123.4	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA24716-625AXSP16	-	82.5	-	-	140.3	-	82.8	-	-	139.5	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA24716-632AXSP16	-	78.8	-	-	135.1	-	79.1	-	-	134.5	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA320P5-425AXSP16	-	76.2	56.3	64.4	131.8	-	76.3	56.7	64.7	131.1	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA320P5-432AXSP16	-	70	51.6	59.2	122.3	-	70.1	52	59.5	121.6	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA320P5-525AXSP16	-	84	62.4	71.3	144.4	-	84.2	62.9	71.7	143.6	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA320P5-532AXSP16	-	78.4	-	66.4	135.8	-	78.5	-	66.7	135.1	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA320P5-625AXSP16	-	92	-	78.3	156.5	-	92.1	-	78.6	155.7	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA320P5-632AXSP16	-	87	-	-	149.8	-	87.2	-	-	148.9	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA320P7-425AXSP16	-	77.5	57.4	65.6	134.3	-	77.7	57.8	66	133.7	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA320P7-432AXSP16	-	71.3	52.6	60.3	124.7	-	71.6	53.1	60.6	124.1	146	12.6	2"	117	10.8	1-1/2"	176	17.8	2"
EAW-VD9102ZA320P7-525AXSP16	-	85.6	63.6	72.5	147	-	85.6	64.1	72.9	146.3	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA320P7-532AXSP16	-	79.7	-	67.6	138.3	-	80	-	68	137.7	180	13.7	2"	144	9	2"	216	19.3	2"
EAW-VD9102ZA320P7-625AXSP16	-	93.6	-	79.7	159.3	-	93.7	-	80.1	158.5	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZA320P7-632AXSP16	-	88.6	-	-	152.4	-	88.9	-	75.6	151.6	225	15.4	2"	180	10.1	2"	270	16.1	3"
EAW-VD9102ZJ177F7-425AXSP16	-	67.7	50.5	57.5	116	-	67.7	50.8	57.7	115.1	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ177F7-432AXSP16	-	62.8	-	53.3	108.6	-	62.9	-	53.5	108	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ177F7-525AXSP16	-	74	-	63	125.5	-	73.8	-	63.1	124.5	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ177F7-532AXSP16	-	69.6	-	-	119.4	-	69.6	-	-	118.4	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ177F7-625AXSP16	-	80	-	-	134.1	-	79.9	-	-	133	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ177F7-632AXSP16	-	76.5	-	-	129.8	-	76.6	-	-	128.6	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ24716-425AXSP16	-	74.1	55.3	63	127.1	-	74.1	55.6	63.1	126.3	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ24716-432AXSP16	-	68.6	50.9	58.2	118.7	-	68.6	51.3	58.4	117.9	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ24716-525AXSP16	-	81.1	60.8	69.1	137.9	-	81.1	61.1	69.2	136.9	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ24716-532AXSP16	-	76.3	-	64.8	130.9	-	76.3	-	64.9	129.9	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ24716-625AXSP16	-	88	-	-	148.1	-	88	-	75.4	146.9	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ24716-632AXSP16	-	84	-	-	147.8	-	84	-	-	141.7	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ320P5-425AXSP16	-	80.9	60.2	68.7	138.8	49.5	80.9	60.5	68.7	137.8	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ320P5-432AXSP16	-	74.5	55.2	63.1	128.8	-	74.5	55.5	63.2	128.1	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ320P5-525AXSP16	-	89.4	66.9	76	152	-	89.2	67.2	76.2	151	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ320P5-532AXSP16	-	83.2	62	70.8	143	-	83.2	62.4	70.9	142.1	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ320P5-625AXSP16	-	97.8	-	83.5	164.7	-	97.7	-	83.6	163.4	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ320P5-632AXSP16	-	92.6	-	78.9	157.6	-	92.5	-	79	156.3	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ320P7-425AXSP16	49.9	82.5	61.4	70	141.5	50.5	82.5	61.7	70.2	140.7	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ320P7-432AXSP16	-	76	56.3	64.4	131.5	-	76	56.7	64.5	130.6	146	13.4	2"	117	11.3	1-1/2"	176	18.8	2"
EAW-VD9102ZJ320P7-525AXSP16	-	91	68.2	77.5	155	-	91	68.4	77.7	154	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ320P7-532AXSP16	-	85	63.3	72.1	145.9	-	84.9	63.6	72.3	145.1	180	14.4	2"	144	9.5	2"	216	20.3	2"
EAW-VD9102ZJ320P7-625AXSP16	-	99.7	-	85.2	168	-	99.6	75.4	85.3	166.8	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9102ZJ320P7-632AXSP16	-	94.4	-	80.5	160.7	-	94.4	-	80.6	159.6	225	16.2	2"	180	10.6	2"	270	17.2	3"
EAW-VD9104PA177F7-425AXSP16	76.3	119.1	91.1	102.3	-	76.5	118.8	91.1	102.2	-	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD9104PA177F7-432AXSP16	70.7	111.2	84.8	95.4	187.7	70.8	110.9	84.6	95.4	186.5	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD9104PA177F7-525AXSP16	82.3	127.4	97.8	109.7	211.1	82.5	127.1	97.7	109.6	209.9	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD9104PA177F7-532AXSP16	77.3	120.8	92.3	103.8	201.7	77.4	120.5	92.2	103.6	200.5	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD9104PA177F7-625AXSP16	89.5	136.9	105.8	118.3	224.2	89.8	136.6	105.7	118.1	222.8	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD9104PA177F7-632AXSP16	85.6	132.3	101.7	114.1	218.3	85.7	132	101.6	113.9	217	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD9104PA24716-425AXSP16	82.5	129.3	98.5	110.8	-	82.6	128.9	98.6	110.8	-	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD9104PA24716-432AXSP16	76.3	120.3	91.5	103.2	-	76.5	120.1	91.4	103	-	113	20.7	1-1/2"	90	13.6	1-1/2"	135	29.1	1-1/2"
EAW-VD9104PA24716-525AXSP16	89.4	138.5	106.1	119.2	-	89.6	138.2	106.3	119.2	-	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD9104PA24716-532AXSP16	83.5	130.7	99.9	112.4	219	83.9	130.5	99.9	112.2	218.3	135	22.1	1-1/2"	108	14.6	1-1/2"	162	26.8	2"
EAW-VD9104PA24716-625AXSP16	97.6	149.7	115.6	129.1	245.6	98	149.2	115.6	129	244.5	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD9104PA24716-632AXSP16	92.9	143.8	110.5	124	238.4	93.1	143.4	110.6	123.8	237.1	169	20	2"	135	16.3	1-1/2"	203	28.1	2"
EAW-VD9104PA320P5-425AXSP16	90.4	142	108.1	121.9	-														

EAW-VD9104P320P7-625AXSP16	119	182	140.5	157	-	119	181.2	140.1	156.5	-	169	21.5	2"	135	17.3	1-1/2"	203	30.2	2"
EAW-VD9104P320P7-632AXSP16	112.3	173.2	133	149.1	-	112.3	172.5	132.7	148.7	-	169	21.5	2"	135	17.3	1-1/2"	203	30.2	2"
EAW-VD9104ZA177F7-425AXSP16	87	135.8	103.9	116.7	226.9	87.1	135.1	103.6	116.3	224.9	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA177F7-432AXSP16	80.2	126.4	96.3	108.4	212.5	80.4	125.7	96.1	108.2	210.7	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA177F7-525AXSP16	96.1	148.4	114.2	127.9	245	96	147.6	113.7	127.2	242.7	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA177F7-532AXSP16	89.8	140.1	107.3	120.6	233.1	89.8	139.4	106.9	120.1	231.1	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA177F7-625AXSP16	105.2	160.6	124.2	138.8	261.5	105.1	159.5	123.7	138	259.1	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA177F7-632AXSP16	99.9	154.2	118.6	132.9	253.3	99.7	153.3	118.1	132.1	251.1	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA24716-425AXSP16	94.8	148	113.1	127.2	-	94.8	147.3	112.9	126.7	-	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA24716-432AXSP16	87.3	137.6	104.8	117.9	231.7	87.4	136.9	104.5	117.5	230	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA24716-525AXSP16	104.7	162.1	124.6	139.7	268.7	104.7	161.4	124.2	139.1	266.3	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA24716-532AXSP16	97.8	152.7	116.9	131.3	254.7	97.7	152.1	116.6	130.8	252.8	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA24716-625AXSP16	115.2	176.2	136.1	152.2	288	115.1	175.1	135.7	151.5	285.3	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA24716-632AXSP16	109	168.7	129.6	145.3	278	109	167.6	129.1	144.8	275.8	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA320P5-425AXSP16	103.2	161.8	123.3	139	-	103.2	160.8	123	138.3	-	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA320P5-432AXSP16	94.6	149.2	113.4	128	-	94.6	148.4	113.2	127.3	-	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA320P5-525AXSP16	115.3	178.8	137.1	153.8	296.8	115.3	177.6	136.7	153.2	294.3	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA320P5-532AXSP16	106.7	167	127.8	143.5	279.8	106.8	166.2	127.2	143.1	277.5	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA320P5-625AXSP16	127.7	195.8	151.2	169.1	321.5	127.7	194.7	150.6	168.2	318.5	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA320P5-632AXSP16	120	185.8	142.9	160.2	307.5	120	184.8	142.3	159.5	304.8	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA320P7-425AXSP16	105.2	164.8	125.7	141.4	-	105.2	163.9	125.2	140.9	-	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA320P7-432AXSP16	96.4	152	115.5	130.4	-	96.4	151.3	115.3	130	-	146	19.5	2"	117	15.3	1-1/2"	176	27.3	2"
EAW-VD9104ZA320P7-525AXSP16	117.2	181.9	139.4	156.6	-	117.3	181.1	139	155.9	300.2	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA320P7-532AXSP16	108.7	170.2	130	146.2	285.1	108.6	169.2	129.6	145.6	282.8	180	20.5	2"	144	13.5	2"	216	28.9	2"
EAW-VD9104ZA320P7-625AXSP16	129.9	199.3	153.9	172.1	327.4	129.9	198.2	153.3	171.2	324.5	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104ZA320P7-632AXSP16	122.1	189.3	145.5	163	313.4	122.1	188.1	145	162.3	310.8	225	22.3	2"	180	14.7	2"	270	25.7	3"
EAW-VD9104Z177F7-425AXSP16	92.3	143.2	109.7	123.1	238	92.2	142.1	109.2	122.4	235.8	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z177F7-432AXSP16	85.2	133.2	101.8	114.5	222.9	85.1	132.3	101.5	113.8	220.9	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z177F7-525AXSP16	102	156.4	120.8	135	257.2	101.8	155.3	120.1	134.1	254.7	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z177F7-532AXSP16	95.3	147.7	113.5	127.2	244.7	95.2	146.7	112.8	126.4	242.3	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z177F7-625AXSP16	111.7	169.3	131.3	146.5	274.4	111.3	167.9	130.6	145.5	271.6	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z177F7-632AXSP16	106.1	162.6	125.5	140.3	265.9	105.7	161.1	124.7	139.4	263.3	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z24716-425AXSP16	100.7	156.5	119.8	134.5	-	100.6	155.4	119.2	133.9	-	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z24716-432AXSP16	92.8	145.3	110.8	124.8	243.6	92.6	144.4	110.3	124.2	241.5	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z24716-525AXSP16	111.5	171.2	132.1	147.8	282.6	111.3	170.3	131.4	146.9	280.2	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z24716-532AXSP16	104	161.5	124	138.9	268.4	104	160.4	123.3	138.4	266	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z24716-625AXSP16	122.5	186.2	144.3	161.1	302.9	122.2	184.8	143.6	160	299.9	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z24716-632AXSP16	116.1	178.2	137.4	153.7	292.5	115.8	176.9	136.7	152.8	289.5	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z320P5-425AXSP16	109.5	170.3	130.4	146.5	-	109.3	169.3	129.7	145.7	-	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z320P5-432AXSP16	100.4	157.2	119.8	134.9	-	100.2	156.4	119.5	134.2	-	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z320P5-525AXSP16	122.4	188.5	144.9	162.3	-	122	186.9	144.2	161.3	-	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z320P5-532AXSP16	113.4	176.1	134.9	151.6	293.5	113.1	175	134.4	150.7	290.7	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z320P5-625AXSP16	135.6	206.3	159.9	178.4	337.1	135.2	204.8	159	177.1	333.8	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z320P5-632AXSP16	127.5	195.9	151	169.2	323.1	127.1	194.5	150.2	168	319.5	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z320P7-425AXSP16	111.6	173.8	133	149.4	-	111.2	172.9	132.3	148.6	-	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z320P7-432AXSP16	102.3	160.3	122.2	137.5	-	102.1	159.3	121.9	136.9	-	146	21	2"	117	16.3	1-1/2"	176	29.5	2"
EAW-VD9104Z320P7-525AXSP16	124.6	192.1	147.6	165.4	-	124.4	190.6	146.9	164.6	-	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z320P7-532AXSP16	115.6	179.6	137.5	154.6	299.6	115.4	178.3	137	153.7	296.9	180	22.1	2"	144	14.6	2"	216	31	2"
EAW-VD9104Z320P7-625AXSP16	138.3	210.4	162.8	181.9	343.9	137.9	208.7	161.9	180.7	340.7	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9104Z320P7-632AXSP16	130	199.9	154	172.3	329.4	129.5	198.3	153.2	171.2	326.3	225	23.8	2"	180	15.7	2"	270	27.9	3"
EAW-VD9106PA177F7-425AXSP12	113.5	176.9	135.2	151.9	-	113.6	176.2	135.1	151.5	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD9106PA177F7-432AXSP12	105.1	165	125.7	141.5	-	105.2	164.3	125.4	141.2	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD9106PA177F7-525AXSP12	124.6	191.9	147.6	165.3	-	124.9	191.1	147.4	165.1	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD9106PA177F7-532AXSP12	117.2	182	139.4	156.4	-	117.3	181.2	139.1	156.2	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD9106PA177F7-625AXSP12	135.8	206.4	159.9	178.3	336.7	136	205.6	159.7	177.9	334.6	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD9106PA177F7-632AXSP12	132.7	201.8	156.2	174.4	-	132.5	200.9	155.7	173.6	-	169	26.9	2"	135	20.8	1-1/2"	203	37.7	2"
EAW-VD9106PA24716-425AXSP12	122.7	191.6	146.4	164.5	-	122.8	191	146.2	164.5	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD9106PA24716-432AXSP12	113.4	178.4	135.6	152.9	-	113.5	177.8	135.5	152.7	-	146	20.1	2"	117	15.6	1-1/2"	176	28.3	2"
EAW-VD9106PA24716-525AXSP12	135.2	208.7	160.3	179.7	-	135.3	208.2	160.2	179.6	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD9106PA24716-532AXSP12	126.7	197	150.6	169.5	-	126.7	196.3	150.6	169.2	-	180	21.1	2"	144	13.9	2"	216	29.7	2"
EAW-VD9106PA24716-625AXSP12	148.1	225.5	174.5	194.8	369.3	148.2	224.7	174.1	194.3	367.2	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD9106PA24716-632AXSP12	140.9	217	166.8	187.1	358.1	141.2	216.1	166.6	186.5	356.1	225	22.8	2"	180	15	2"	270	26.7	3"
EAW-VD9106PA320P5-425AXSP08	130.2	208.2	157.8	178.3	353.8	131.1	208.2	158.2	178.3	352.2	225	16.7	2"	180	11	2"	270	18.2	3"
EAW-VD91																			

EAW-VD9106ZA177F7-532AXSP16	139.6	214	164.9	184.6	-	139	212.2	163.7	183.3	-	180	27.4	2"	144	18.1	2"	216	38.4	2"
EAW-VD9106ZA177F7-625AXSP16	163.4	244.8	190.8	212	-	162.5	242.7	189.4	210.4	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD9106ZA177F7-632AXSP16	155.4	235	182.3	203.2	-	154.7	233.3	181.2	202	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD9106ZA24716-425AXSP12	146.9	228.2	174.7	196.4	-	146.8	226.9	174.1	195.2	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD9106ZA24716-432AXSP12	135.8	212.3	162.1	182.3	-	135.6	211.1	161.6	181.5	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD9106ZA24716-525AXSP12	161.6	248.3	191.2	214	409.3	161.5	246.8	190.6	212.9	406.2	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD9106ZA24716-532AXSP12	151.1	234.4	179.8	201.5	389.6	150.9	233	179.1	200.6	386.1	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD9106ZA24716-625AXSP12	175.7	266.9	207	230.8	434.5	175.5	265	206	229.7	430.9	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD9106ZA24716-632AXSP16	169.4	257.2	199	222.4	-	168.7	255.1	197.9	220.9	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD9106ZA320P5-425AXSP12	160.2	249.3	190.8	214.4	-	160	248	189.9	213.3	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD9106ZA320P5-432AXSP12	147	230.4	175.6	197.7	-	146.7	229	175	196.9	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD9106ZA320P5-525AXSP12	177.6	273.7	210.4	236	-	177.5	272.2	209.6	234.7	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD9106ZA320P5-532AXSP12	165.1	256.5	196.4	220.4	-	164.9	254.8	195.5	219.6	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD9106ZA320P5-625AXSP12	194.8	296.7	229.7	256.4	485.8	194.5	294.7	228.5	255	481.2	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD9106ZA320P5-632AXSP16	186.3	283.9	219.3	245	-	185.4	281.4	217.7	243.2	-	225	29.1	2"	180	19.2	2"	270	35.3	3"
EAW-VD9106ZA320P7-425AXSP12	163	253.9	194.2	218.3	-	162.9	252.7	193.4	217.3	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD9106ZA320P7-432AXSP12	149.7	234.8	178.9	201.4	-	149.6	233.6	178.2	200.7	-	203	22.1	2"	162	14.6	2"	244	26.5	3"
EAW-VD9106ZA320P7-525AXSP12	180.9	278.9	214.3	240.1	-	180.5	277.1	213.6	238.9	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD9106ZA320P7-532AXSP12	168.2	261.2	199.8	224.7	-	167.7	259.5	199.3	223.6	-	248	19.3	3"	198	15.8	2"	298	27.1	3"
EAW-VD9106ZA320P7-625AXSP12	198.2	302	233.7	260.9	494.6	198	300.1	232.5	259.6	490.2	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD9106ZA320P7-632AXSP12	186.7	287.2	221	247.4	473.8	186.3	285.3	220.2	246.4	469.8	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD9106Z1177F7-425AXSP12	143	220	169.2	189.7	-	142.5	218.2	168.4	188.5	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z1177F7-432AXSP12	132.2	205.1	157.2	176.6	-	131.9	203.6	156.6	175.5	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z1177F7-525AXSP12	157	239	184.9	206.5	391.5	156.5	237	183.9	205.1	387.7	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z1177F7-532AXSP12	147	226	174.1	195	373.4	146.5	224.5	173.2	193.6	369.3	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z1177F7-625AXSP12	170.2	256.1	199.6	222	414.4	169.4	254	198.2	220.4	409.6	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9106Z1177F7-632AXSP16	164.2	247.3	192.2	214.1	-	163.1	245.1	190.7	212.2	-	225	31.4	2"	180	20.7	2"	270	38.5	3"
EAW-VD9106Z24716-425AXSP12	156	241	185	207.4	-	155.3	239.2	184	206.2	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z24716-432AXSP12	143.9	223.9	171.3	192.7	-	143.5	222.4	170.5	191.3	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z24716-525AXSP12	171.6	262.2	202.4	226.2	-	171.1	260.3	201.5	224.9	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z24716-532AXSP12	160.6	247.4	190.3	213.1	409.9	160.1	245.6	189.2	211.8	405.6	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z24716-625AXSP12	186.8	281.7	219.1	243.8	457	186	279.5	217.7	242.2	452.5	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9106Z24716-632AXSP12	177	269.8	208.8	233.2	441.9	176.3	267.7	207.5	231.7	437.4	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9106Z320P5-425AXSP12	169.4	262.5	201.2	225.8	-	169	260.5	200	224.4	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z320P5-432AXSP12	155.6	242.5	185.5	208.5	-	155.2	240.8	184.5	207.4	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z320P5-525AXSP12	188.3	288.4	222.2	248.7	-	187.6	286	221	246.9	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z320P5-532AXSP12	175	270	207.3	233.3	-	174.1	267.8	206.3	230.8	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z320P5-625AXSP12	206.6	312.6	242.5	270.5	-	205.7	310	240.8	268.5	503.7	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9106Z320P5-632AXSP12	194.4	297.1	229.2	256.3	488.3	193.6	294.6	228	254.5	482.8	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9106Z320P7-425AXSP08	165.2	261.5	199.1	224.2	439.5	165.6	260.1	198.5	223.3	436.2	304	14.9	3"	244	9.9	3"	365	21	3"
EAW-VD9106Z320P7-432AXSP12	158.5	247.5	189.1	212.7	-	158.2	245.8	188.2	211.6	-	203	23.8	2"	162	15.7	2"	244	28.9	3"
EAW-VD9106Z320P7-525AXSP12	191.8	293.9	226.7	253.7	-	191.1	291.6	225.2	252.1	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z320P7-532AXSP12	178.3	275.4	211.3	236.9	-	177.6	273.3	210.4	235.5	-	248	21	3"	198	17	2"	298	29.5	3"
EAW-VD9106Z320P7-625AXSP12	210.3	318.8	247.2	275.4	-	209.7	315.9	245.6	273.5	-	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9106Z320P7-632AXSP12	198	302.8	233.8	261.5	497.9	197.2	300.3	232.3	259.7	492.5	304	21.6	3"	244	14.3	3"	365	30.3	3"
EAW-VD9108PA177F7-425AXSP08	151.8	237.4	181.2	203.9	-	152.3	236.5	181.1	203.5	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA177F7-432AXSP08	140.6	221.6	168.9	190.2	373.6	140.9	220.7	168.5	189.7	371.2	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA177F7-525AXSP08	167.8	259.1	199.3	223.4	429.3	168.1	258.4	199	223.1	426.9	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD9108PA177F7-532AXSP08	157.6	246.1	188.4	211.7	410.9	158	245.4	188.2	211.4	408.4	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD9108PA177F7-625AXSP12	184.7	278	216.1	240.9	-	184.6	276.9	215.5	240	-	225	27.9	2"	180	18.4	2"	270	33.9	3"
EAW-VD9108PA177F7-632AXSP08	170.3	263.6	202.5	227.2	435.4	170.6	262.8	202.5	226.8	433	338	17.5	3"	270	11.6	3"	406	24.6	3"
EAW-VD9108PA24716-425AXSP08	164.3	257.2	196.3	220.9	-	164.7	256.9	196	220.5	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA24716-432AXSP08	151.8	239.6	182	205.1	-	152.3	238.9	182	205.2	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA24716-525AXSP08	182.4	282.3	216.4	243	468.9	182.8	281.7	216.6	242.7	466.4	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD9108PA24716-532AXSP08	170.8	267	204.1	229.2	446.5	171.1	266.4	204	229	444	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD9108PA24716-625AXSP08	194.4	298.3	230.3	257.5	490	195.1	297.7	230.2	257	487.3	338	17.5	3"	270	11.6	3"	406	24.6	3"
EAW-VD9108PA24716-632AXSP08	184.9	286.8	220.4	247.2	474.9	185.6	286.1	220.1	246.5	472.3	338	17.5	3"	270	11.6	3"	406	24.6	3"
EAW-VD9108PA320P5-425AXSP08	179.9	283.1	215.4	242.8	-	180.3	282	215.4	242.2	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA320P5-432AXSP08	165.3	261.3	198.5	224	-	165.8	260.9	198.4	223.6	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA320P5-525AXSP08	201.5	313.2	239.9	269.3	-	202	312.4	239.7	269	-	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD9108PA320P5-532AXSP08	188	294	224.5	252.5	-	188.2	293.2	224.4	252.2	-	282	16.9	3"	225	14.9	2"	338	23.8	3"
EAW-VD9108PA320P5-625AXSP08	217.1	333.7	257.1	287.9	550.4	217.9	333	257	287.7	547.8	338	17.5	3"	270	11.6	3"	406	24.6	3"
EAW-VD9108PA320P5-632AXSP08	204.8	318.3	244	273.6	528.7	205.2	317.4	243.7	273.3	526.4	338	17.5	3"	270	11.6	3"	406	24.6	3"
EAW-VD9108PA320P7-425AXSP08	182.6	287.4	218.6	246.4	-	183.1	286.4	218.6	245.9	-	225	20.1	2"	180	13.3	2"	270	23	3"
EAW-VD9108PA320P7-432AXSP08	167.7	265.3	201.3	227.3	-														

EAW-VD9108ZA24716-525AXSP08	212.4	328.3	252.6	282.8	543	212.4	326.8	251.9	281.8	538.8	372	18.1	3"	298	11.9	3"	446	25.4	3"
EAW-VD9108ZA24716-532AXSP12	205.6	315.9	243.4	272.6	-	205	313.9	241.9	270.9	-	248	24.4	3"	198	19.2	2"	298	34.3	3"
EAW-VD9108ZA24716-625AXSP12	239.1	359.5	279.7	311.3	-	238.2	356.8	278	309.4	-	304	25	3"	244	16.5	3"	365	35.1	3"
EAW-VD9108ZA24716-632AXSP12	227.2	344.7	266.9	297.8	-	226.2	341.9	265.4	295.7	-	304	25	3"	244	16.5	3"	365	35.1	3"
EAW-VD9108ZA320P5-425AXSP08	210.8	329.6	251.7	282.9	-	210.6	328	251	282	-	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD9108ZA320P5-432AXSP08	193.1	304.4	231.7	261.1	-	193.3	302.7	231	260	-	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD9108ZA320P5-525AXSP08	233.7	361.8	277.8	311.8	600.8	233.6	359.8	276.8	310.1	595.7	372	18.1	3"	298	11.9	3"	446	25.4	3"
EAW-VD9108ZA320P5-532AXSP08	216.6	338.8	259.2	291.4	567.1	216.7	337.1	258.4	290	562.3	372	18.1	3"	298	11.9	3"	446	25.4	3"
EAW-VD9108ZA320P5-625AXSP08	254.2	390.5	301.2	336.8	640.7	254.3	387.9	300.4	335.4	635.6	451	19.2	3"	361	12.7	3"	541	23.5	4"
EAW-VD9108ZA320P5-632AXSP12	249.5	380.1	293.8	328.6	-	248.7	377.2	292	326.1	-	304	25	3"	244	16.5	3"	365	35.1	3"
EAW-VD9108ZA320P7-425AXSP08	214.4	335.7	256.1	288.5	-	214.4	333.7	255.6	287.2	-	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD9108ZA320P7-432AXSP08	196.7	310.2	235.9	265.9	-	196.8	308.6	235.3	265	-	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD9108ZA320P7-525AXSP08	238	368.7	283	317.2	612.6	237.6	366.4	282.1	316.1	607.7	372	18.1	3"	298	11.9	3"	446	25.4	3"
EAW-VD9108ZA320P7-532AXSP08	220.6	344.9	263.6	296.5	577.7	220.9	343.3	262.9	295.6	573	372	18.1	3"	298	11.9	3"	446	25.4	3"
EAW-VD9108ZA320P7-625AXSP08	258.9	397	306.4	342.7	652.4	258.7	395	305.3	341.4	647.4	451	19.2	3"	361	12.7	3"	541	23.5	4"
EAW-VD9108ZA320P7-632AXSP08	243.1	377.1	289.7	324.9	625.1	243	375.1	288.7	323.2	619.2	451	19.2	3"	361	12.7	3"	541	23.5	4"
EAW-VD9108ZJ177F7-425AXSP08	188.1	291.2	223.4	250.6	483.2	187.5	289.3	222.4	249.4	478.6	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ177F7-432AXSP08	173.7	271.3	207.7	233.4	453.9	173.4	269.7	206.6	232	449.6	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ177F7-525AXSP08	206.5	316.6	244.4	273.1	519.4	205.9	313.9	243.1	271.5	514.4	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ177F7-532AXSP08	193.2	299.2	229.9	258	495.3	192.8	297.2	228.8	256.3	490.4	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ177F7-625AXSP12	231.4	344.8	269.2	299.3	-	229.7	341.5	267.3	296.4	-	304	27.3	3"	244	18	3"	365	38.3	3"
EAW-VD9108ZJ177F7-632AXSP12	220.1	331.4	257.7	287	-	218.7	328.1	255.7	284.4	-	304	27.3	3"	244	18	3"	365	38.3	3"
EAW-VD9108ZJ24716-425AXSP08	205.4	318.3	244.2	273.9	-	205	316.5	242.9	272.7	-	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ24716-432AXSP08	189.3	296.1	226.3	254.1	496.3	189.2	294.1	225.2	252.8	491.9	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ24716-525AXSP08	226.1	346.8	267.4	299.1	571.7	225.4	344.7	266.3	297.7	566	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ24716-532AXSP08	211.2	327.5	251.3	281.9	543.5	210.7	325.1	250.3	280.2	538.6	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ24716-625AXSP08	244.3	371	287.8	320.9	604.4	243.7	368.2	286	318.8	598.5	451	20.8	3"	361	13.7	3"	541	25.6	4"
EAW-VD9108ZJ24716-632AXSP12	240.5	363.6	282	314.4	-	239.1	360.2	280.1	311.9	-	304	27.3	3"	244	18	3"	365	38.3	3"
EAW-VD9108ZJ320P5-425AXSP08	223	347.2	265.5	298.6	-	222.5	344.6	264.4	296.8	-	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ320P5-432AXSP08	204.9	321.1	244.9	275.5	-	204.5	318.9	243.7	274	-	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ320P5-525AXSP08	248.3	381.8	293.5	329.1	-	247.4	378.6	292	326.8	-	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ320P5-532AXSP08	230.1	357.2	274.1	307.3	594.6	229.4	354.9	272.4	305.8	588.8	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ320P5-625AXSP08	270.1	411.6	318.5	355.4	672.6	269.3	408.1	316.7	353.3	665.3	451	20.8	3"	361	13.7	3"	541	25.6	4"
EAW-VD9108ZJ320P5-632AXSP08	253.8	390.8	301.1	336.9	643.7	253.1	387.5	299.5	334.9	637.3	451	20.8	3"	361	13.7	3"	541	25.6	4"
EAW-VD9108ZJ320P7-425AXSP08	227.4	354.4	270.8	304.6	-	227	351.9	269.8	302.9	-	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ320P7-432AXSP08	208.8	327	249.7	280.9	-	208.4	325.5	248.5	279.5	-	304	18.8	3"	244	12.4	3"	365	26.3	3"
EAW-VD9108ZJ320P7-525AXSP08	252.9	389.1	299.4	335.3	-	252	386.1	298	333.1	-	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ320P7-532AXSP08	234.5	364.3	279.3	313.3	606.9	233.9	361.7	277.8	311.4	601.3	372	19.6	3"	298	12.9	3"	446	27.5	3"
EAW-VD9108ZJ320P7-625AXSP08	275.3	419.2	324.6	362.3	686.1	274.6	416.4	323	359.9	679.1	451	20.8	3"	361	13.7	3"	541	25.6	4"
EAW-VD9108ZJ320P7-632AXSP08	258.8	398.2	306.7	343.1	657.2	258.2	395.5	305.1	341.3	650.1	451	20.8	3"	361	13.7	3"	541	25.6	4"
EAW-VD9110PA177F7-425AXSP08	193.3	299.7	229.8	258	-	193.2	298.5	229.2	257.3	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD9110PA177F7-432AXSP08	179.2	280	213.7	240.4	-	179.1	278.8	213.1	239.7	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD9110PA177F7-525AXSP08	213.7	327.6	252.5	282.6	-	213.7	326.2	251.8	281.7	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD9110PA177F7-532AXSP08	201.2	310.9	238.7	267.6	-	201.3	309.6	238.5	266.8	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD9110PA177F7-625AXSP08	227.7	344.5	267.2	298	561.8	227.9	343.1	266.9	297.2	558.4	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA177F7-632AXSP08	217.9	332.7	256.9	287.3	547	217.8	331.7	256.5	286.4	543.9	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA24716-425AXSP06	199.8	314.5	239.4	269.6	-	200.8	314.1	239.7	269.8	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD9110PA24716-432AXSP08	193.3	302.9	230.8	260	-	193.4	301.9	230.5	259	-	225	23.6	2"	180	15.5	2"	270	27.8	3"
EAW-VD9110PA24716-525AXSP08	232.1	356.5	274.4	307.5	-	232.2	355.1	273.8	306.6	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD9110PA24716-532AXSP08	217.8	336.9	258.7	290.3	-	217.7	336.2	258.2	289.6	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD9110PA24716-625AXSP08	248	376.8	291.6	325.5	-	248.1	375.5	291	324.8	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA24716-632AXSP08	236.4	362.1	278.9	312.2	-	236.4	360.6	278.5	311.3	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA320P5-425AXSP06	218.9	345.8	262.6	296.1	-	219.7	345.2	262.6	296.1	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD9110PA320P5-432AXSP06	200.9	319.1	241.9	273	-	201.7	318.6	241.9	272.9	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD9110PA320P5-525AXSP06	248.4	386.7	295.8	332.8	-	249.1	385.8	295.7	332.5	-	372	16.6	3"	298	11	3"	446	23.4	3"
EAW-VD9110PA320P5-532AXSP08	239	371.7	284.3	319.6	-	239.2	370.1	284	318.6	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD9110PA320P5-625AXSP08	276.3	421.6	325.7	364	-	276.5	420.2	325.5	363.2	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA320P5-632AXSP08	261.1	402	308.9	346.3	-	261.2	400.2	308.6	345.3	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA320P7-425AXSP06	222.2	351	266.6	300.5	-	222.9	349.9	267	300.6	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD9110PA320P7-432AXSP06	203.9	323.9	245.3	277.2	-	204.6	323.6	245.5	277	-	293	15.7	3"	234	14.4	2"	352	22.1	3"
EAW-VD9110PA320P7-525AXSP06	252	392.7	300.2	337.8	-	252.7	391.8	300.6	337.5	-	372	16.6	3"	298	11	3"	446	23.4	3"
EAW-VD9110PA320P7-532AXSP08	242.3	377.2	288.3	324.2	-	242.7	375.8	288.2	323.4	-	282	20.4	3"	225	17.2	2"	338	28.6	3"
EAW-VD9110PA320P7-625AXSP08	280.8	428.6	330.9	369.9	-	280.7	426.9	330.5	368.9	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-VD9110PA320P7-632AXSP08	264.9	408.1	313.5	351.5	-	265	406.4	313.1	350.4	-	338	21	3"	270	13.8	3"	406	29.4	3"
EAW-																			

EAW-VD9110ZA320P5-432AXSP08	246.2	384.7	293.8	330.1	-	245.5	382.4	292.2	328.7	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD9110ZA320P5-525AXSP08	297.4	457.5	352.3	394	-	296.7	454.3	350.4	391.8	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD9110ZA320P5-532AXSP08	276.6	428.2	328.5	368.6	-	275.7	425.4	326.9	366.7	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD9110ZA320P5-625AXSP08	324.7	492.6	381.8	426.2	-	323.8	489.3	379.8	423.3	-	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD9110ZA320P5-632AXSP08	305.7	467.9	360.6	403.6	-	304.8	464.5	359.1	401.2	-	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD9110ZA320P7-425AXSP06	265.5	416.8	317.8	358.1	-	266	415.1	317.1	356.5	-	406	17.2	3"	325	11.3	3"	487	24.2	3"
EAW-VD9110ZA320P7-432AXSP08	250.6	392	299	336.9	-	250.1	390	297.7	335.1	-	304	20.7	3"	244	13.6	3"	365	29	3"
EAW-VD9110ZA320P7-525AXSP08	302.9	465.6	358.3	401.4	-	302.4	462.6	356.5	399.4	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD9110ZA320P7-532AXSP08	281.3	435.9	334.2	375.1	-	281	433.2	332.7	373.2	-	372	21.5	3"	298	14.2	3"	446	30.2	3"
EAW-VD9110ZA320P7-625AXSP08	329.9	501.4	388.5	433.1	-	329	498.2	386.5	430.8	-	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD9110ZA320P7-632AXSP08	310.7	476	367.2	411.1	-	310	472.8	365.3	408.2	-	451	22.7	3"	361	14.9	3"	541	28.3	4"
EAW-VD9110Z177F7-425AXSP08	239.1	367.2	282.9	316.7	-	238.3	364.3	281.1	314.6	-	304	22.6	3"	244	14.9	3"	365	31.6	3"
EAW-VD9110Z177F7-432AXSP08	221.6	342.5	262.9	294.8	-	220.7	339.9	261.4	293	-	304	22.6	3"	244	14.9	3"	365	31.6	3"
EAW-VD9110Z177F7-525AXSP08	263.1	399.4	309.1	345.2	-	261.9	396	306.9	342.2	-	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z177F7-532AXSP08	246.6	377.8	291.1	325.5	-	245.6	374.1	289.1	323.2	615.4	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z177F7-625AXSP08	283.7	425.4	331.8	369	687.6	282.3	421.9	329.4	365.9	680.5	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z177F7-632AXSP08	269.4	408.5	316.7	353.5	666.4	268.1	404.9	314.4	350.4	658.9	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z24716-425AXSP08	260.8	402.2	308.9	346.2	-	259.7	398.7	307.2	344.2	-	304	22.6	3"	244	14.9	3"	365	31.6	3"
EAW-VD9110Z24716-432AXSP08	240.8	373.9	286	321.7	-	240	370.7	284.6	319.4	-	304	22.6	3"	244	14.9	3"	365	31.6	3"
EAW-VD9110Z24716-525AXSP08	287.4	437.6	338.3	378.2	-	286	434.4	336.2	375.3	-	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z24716-532AXSP08	268.9	413	318.2	356.2	-	267.7	409.9	315.9	353.5	-	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z24716-625AXSP08	310.9	467.8	364.1	405.3	-	309.6	464.2	361.3	402.2	750.6	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z24716-632AXSP08	294.9	447.9	346.5	387	732.9	293.4	443.9	344.3	384	725.4	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z320P5-425AXSP06	276.8	431.3	329.5	370.7	-	276.2	428.7	328.2	368.5	-	406	18.6	3"	325	12.3	3"	487	26.2	3"
EAW-VD9110Z320P5-432AXSP08	260.4	404.9	309.7	348.2	-	259.6	402	308.1	345.6	-	304	22.6	3"	244	14.9	3"	365	31.6	3"
EAW-VD9110Z320P5-525AXSP08	314.8	481.3	371.4	415.7	-	313.6	477.3	368.9	412.8	-	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z320P5-532AXSP08	292.7	450.6	346.6	388.5	-	291.2	447	344.4	385.3	-	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z320P5-625AXSP08	343.4	519.1	403.1	449	-	341.8	514.7	400.2	445.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z320P5-632AXSP08	323.1	492.5	380.9	425.4	-	321.7	488.3	378.3	422.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z320P7-425AXSP06	282.1	440.1	336	378.2	-	281.7	437	334.9	376	-	406	18.6	3"	325	12.3	3"	487	26.2	3"
EAW-VD9110Z320P7-432AXSP06	258.7	406.6	309.6	348.5	-	258.3	404	308.3	347.4	-	406	18.6	3"	325	12.3	3"	487	26.2	3"
EAW-VD9110Z320P7-525AXSP06	317.1	489.1	376	421.6	809.5	316.5	486	374.2	418.9	801.9	507	20.3	3"	406	13.4	3"	609	24.1	4"
EAW-VD9110Z320P7-532AXSP08	298.3	459.7	353.3	396.1	-	297	456.2	351.3	393.1	-	372	23.4	3"	298	15.4	3"	446	32.8	3"
EAW-VD9110Z320P7-625AXSP08	350.1	528.7	410.3	457.8	-	348.1	524.5	407.6	454.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9110Z320P7-632AXSP08	329.5	502.6	388	434	-	327.7	498.5	385.4	430.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9112PA177F7-425AXSP06	225.7	351.5	268.9	302.2	-	226	350.8	268.4	301.5	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD9112PA177F7-432AXSP06	209	327.6	249.7	281.4	-	209.2	326.9	249.3	280.7	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD9112PA177F7-525AXSP06	252.5	388.2	298.9	334.6	-	252.5	386.6	298.1	333.7	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA177F7-532AXSP06	237.3	368.6	282.2	317	613.7	237.4	367	281.9	316.1	610.1	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA177F7-625AXSP08	276.2	416.5	323.7	360.5	-	276.1	414.3	322.8	359	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD9112PA177F7-632AXSP08	264.3	401.9	311.1	347.3	-	264.1	400.2	310.1	346.1	-	338	24.4	3"	270	16.1	3"	406	34.2	3"
EAW-VD9112PA24716-425AXSP06	243.6	381.3	290.6	327.1	-	244.2	380.2	290.8	326.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD9112PA24716-432AXSP06	225.3	354.1	269.6	303.9	-	225.5	353	269.3	303.6	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD9112PA24716-525AXSP06	273.6	422.3	324.7	363.9	-	274.2	421.3	324.4	363	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA24716-532AXSP06	256.7	399.2	305.6	343.2	-	257.1	397.7	305	342.4	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA24716-625AXSP06	294.6	449.2	346.9	387.9	736	295.2	447.7	346.8	387.1	731.8	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD9112PA24716-632AXSP06	280	431.5	332.1	371.9	713.3	280.6	430.3	331.7	370.8	709.4	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD9112PA320P5-425AXSP04	257.8	412.7	312.3	353.3	701.8	259.6	412.7	313.2	353.3	698.9	451	14.7	3"	361	9.7	3"	541	17.3	4"
EAW-VD9112PA320P5-432AXSP06	245.1	386.6	293.8	331.5	-	245.3	385.3	293.5	330.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD9112PA320P5-525AXSP06	302.8	469	359.2	403.2	-	303.1	467.2	359	402.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA320P5-532AXSP06	281.9	439.5	336.2	378.1	-	282.3	438.3	335.3	377	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA320P5-625AXSP06	328.1	502.5	387.4	433.7	-	328.8	500.8	387.2	432.8	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD9112PA320P5-632AXSP06	309.7	478.8	367.7	412.4	-	310.4	476.8	367.3	411.1	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD9112PA320P7-425AXSP04	261.6	418.9	317.1	358.5	713.1	263.6	419.1	317.8	358.6	710.3	451	14.7	3"	361	9.7	3"	541	17.3	4"
EAW-VD9112PA320P7-432AXSP06	248.7	392.6	298.3	336.3	-	249.2	391.4	297.8	335.9	-	293	18.3	3"	234	16.1	2"	352	25.7	3"
EAW-VD9112PA320P7-525AXSP06	307.2	475.6	364.5	409.3	-	307.5	474.4	364.3	408.9	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA320P7-532AXSP06	285.8	445.9	340.9	383.5	-	286.3	445.1	340.2	382.7	-	372	19.2	3"	298	12.7	3"	446	27	3"
EAW-VD9112PA320P7-625AXSP06	333.4	510.9	393.6	440.8	-	333.9	508.8	393.2	439.5	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD9112PA320P7-632AXSP06	314.2	486.1	373.1	418.5	-	314.9	484.1	372.7	417.3	-	451	20.4	3"	361	13.4	3"	541	25.2	4"
EAW-VD9112P177F7-425AXSP06	241.2	374.4	286.7	321.9	-	241.1	372.3	286	321	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD9112P177F7-432AXSP06	223.2	348.5	266.1	299.4	-	223.2	346.7	265.7	298.2	-	293	20	3"	234	17.2	2"	352	28.1	3"
EAW-VD9112P177F7-525AXSP06	270.4	414	319.4	356.8	-	270	411.8	318.1	355.8	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD9112P177F7-532AXSP06	254.4	392.6	301.3	338.1	-	254	390.1	300.3	336.5	-	372	20.9	3"	298	13.8	3"	446	29.4	3"
EAW-VD9112P177F7-625AXSP06	290.4	439	340.8	380	714.6	290.3	437.1	339.8	378.4	709.2	451	22.1	3"	361	14.5	3"	541	27.6	4"
EAW-VD9112P177F7-632AXSP06	276.8	423.3	326.8	365.4	694.5	276.8	420.8	325.8	363.7	689.6	451	22.1	3"	3					

EAW-VD9112ZA320P7-425AXSP06	324.1	505.2	386.3	434.2	-	323.4	502.2	384.7	432.3	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD9112ZA320P7-432AXSP06	297.3	467	355.6	400.4	-	297	463.8	354.4	399	-	406	19.8	3"	325	13	3"	487	27.8	3"
EAW-VD9112ZA320P7-525AXSP06	364.1	561.1	431.9	483.9	-	364	558.2	429.8	481.4	-	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD9112ZA320P7-532AXSP06	338.8	526.4	403.1	452.3	-	338.4	523.1	401.2	450.1	-	507	21.5	3"	406	14.1	3"	609	25.7	4"
EAW-VD9112ZA320P7-625AXSP06	394.7	600.9	464.9	519	984.5	393.7	597.8	463.2	516.3	976.9	609	19	4"	487	15.4	3"	730	26.6	4"
EAW-VD9112ZA320P7-632AXSP06	371.1	571.2	440	492.5	943.8	370.2	567.4	437.7	489.9	934.9	609	19	4"	487	15.4	3"	730	26.6	4"
EAW-VD9112Z177F7-425AXSP06	284.1	438	336.8	377.1	-	283.2	434.6	334.7	374.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z177F7-432AXSP06	263	408.3	312.7	351.3	-	262	405.3	310.9	349.2	674.5	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z177F7-525AXSP06	316.2	481.2	372.5	416	787.8	314.8	477.1	369.8	412.9	779.1	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z177F7-532AXSP06	296.4	455.3	350.9	392.9	751.8	295.2	451.5	349.1	390.2	743.4	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z177F7-625AXSP08	344	513.5	400.7	445.6	-	341.9	508.6	397.9	441.9	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD9112Z177F7-632AXSP08	327.4	493.4	383.3	427.1	-	325.3	488.4	379.9	423.3	-	451	28.4	3"	361	18.7	3"	541	36.3	4"
EAW-VD9112Z24716-425AXSP06	309.8	479	367.6	412.1	-	309.1	475.5	365.6	409.7	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z24716-432AXSP06	286.2	444.9	340.7	382.6	-	285.4	441.9	339	380.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z24716-525AXSP06	345.9	527.3	407.7	455.7	-	344.7	523.4	405.3	452.9	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z24716-532AXSP06	323.8	498.5	383.1	429.5	824.2	322.9	494.8	381.4	426.8	816.6	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z24716-625AXSP06	371.5	561.4	435.8	485.7	910.8	370	556.4	433.6	482.6	901.8	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD9112Z24716-632AXSP06	351.8	537.5	415.8	463.8	879.5	351.1	532.7	413.1	460.8	871.6	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD9112Z320P5-425AXSP06	337	521.7	400.4	449.4	-	335.6	518.5	398	446.6	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z320P5-432AXSP06	309.4	482.5	368.8	414.7	-	308.5	479.2	367	411.8	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z320P5-525AXSP06	379	580.8	447.8	501.1	-	377.4	575.9	445.4	497.5	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z320P5-532AXSP06	352.4	544	418	468.5	-	351.2	539.6	415.3	465.3	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z320P5-625AXSP06	411	622.1	482.4	538.1	1014.8	409.6	616.8	479.6	534.2	1003.9	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD9112Z320P5-632AXSP06	386.5	591	456.4	510.4	971.7	384.9	585.9	453.2	506.7	962	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD9112Z320P7-425AXSP06	343.6	532.5	408.3	458.5	-	342.3	528.6	406.1	455.1	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z320P7-432AXSP06	315.2	492.3	375.9	422.9	-	314.5	489.1	374.2	420	-	406	21.5	3"	325	14.2	3"	487	30.2	3"
EAW-VD9112Z320P7-525AXSP06	386.6	592	456.1	510.5	-	385.2	587.3	453.9	507.1	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z320P7-532AXSP06	359.2	555	426.2	477.7	-	358.2	558.8	423.7	474.8	-	507	23.2	3"	406	15.3	3"	609	28.1	4"
EAW-VD9112Z320P7-625AXSP06	418.9	634.4	491.7	548.6	-	417.2	629.4	489.1	544.9	-	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD9112Z320P7-632AXSP06	394.2	602.3	464.9	520	992	392.7	598.2	462.5	516.4	981.3	609	20.7	4"	487	16.6	3"	730	29	4"
EAW-VD9114PA177F7-425AXSP04	258.8	408.1	310.9	350.1	687.6	259.8	407.9	311.4	350.6	683.8	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA177F7-432AXSP06	246.6	385	294	330.9	-	246.6	383.4	293.2	330	-	293	20.9	3"	247	17.8	2"	352	29.3	3"
EAW-VD9114PA177F7-525AXSP06	297.8	456.1	351.4	393.3	-	297.8	454.1	350.9	392.1	-	372	21.8	3"	298	14.4	3"	446	30.6	3"
EAW-VD9114PA177F7-532AXSP06	280.2	432.6	332	372.2	-	280.4	430.8	331.6	371.1	-	372	21.8	3"	298	14.4	3"	446	30.6	3"
EAW-VD9114PA177F7-625AXSP06	319.2	482.2	374.6	417.2	-	319.1	480.4	373.6	416.1	-	451	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114PA177F7-632AXSP06	305	465.8	359.7	402.2	-	305	463.7	358.6	401	-	451	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114PA24716-425AXSP04	280.3	442.6	336.5	379.6	747.2	281.6	442	336.8	379.7	743.5	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA24716-432AXSP04	258.5	411.5	312.2	352.7	698.9	259.8	411.1	312.6	352.8	696.3	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA24716-525AXSP06	322.8	496.2	381.8	427.8	-	323	494.3	381.5	426.7	-	372	21.8	3"	298	14.4	3"	446	30.6	3"
EAW-VD9114PA24716-532AXSP06	302.8	468.7	359.7	403.8	-	303.2	467	358.9	402.8	-	372	21.8	3"	298	14.4	3"	446	30.6	3"
EAW-VD9114PA24716-625AXSP06	347.6	526.8	408.2	455.7	-	347.3	525	407.4	454.7	-	451	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114PA24716-632AXSP06	330.9	507	390.5	437.1	-	330.9	504.8	390	435.8	-	451	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114PA320P5-425AXSP04	307.4	486.7	369.6	416.9	-	308.8	485.8	369.7	416.9	-	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA320P5-432AXSP04	282	449.2	340.2	384.7	-	283.3	448.7	340.5	384.5	-	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA320P5-525AXSP04	344.1	539.7	412.1	463.6	903.4	345.8	538.6	412.6	463.3	898.5	564	14.7	4"	451	12.1	3"	676	20.7	4"
EAW-VD9114PA320P5-532AXSP04	320.1	505.8	384.9	434.1	853.3	321.3	505.5	385.5	433.7	849.4	564	14.7	4"	451	12.1	3"	676	20.7	4"
EAW-VD9114PA320P5-625AXSP06	386.8	590.2	455.9	509.6	-	387.1	588.2	455	508.4	-	541	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114PA320P5-632AXSP06	365.6	561.9	432.5	484.8	-	365.6	560.3	432	483.4	-	451	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114PA320P7-425AXSP04	312.1	494.1	374.8	423.1	-	313.3	493.4	375.2	423.2	-	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA320P7-432AXSP04	286.1	456.2	345.3	390.2	-	287.4	455.7	345.6	390.3	-	451	16.5	3"	361	10.8	3"	541	19.7	4"
EAW-VD9114PA320P7-525AXSP04	349.1	548	418.1	470.6	917.8	350.8	546.8	418.7	470.2	912.7	564	14.7	4"	451	12.1	3"	676	20.7	4"
EAW-VD9114PA320P7-532AXSP04	324.5	513.2	390.3	440.2	866.3	325.9	513.2	391.1	440.1	862.9	564	14.7	4"	451	12.1	3"	676	20.7	4"
EAW-VD9114PA320P7-625AXSP04	376.5	585.5	449	503.9	969.7	377.8	584.1	449.3	503.3	964.7	676	15.5	4"	541	10.2	4"	812	21.8	4"
EAW-VD9114PA320P7-632AXSP06	370.9	570.5	438.9	492.1	-	371	568.1	438.4	490.6	-	451	22.9	3"	361	15.1	3"	541	28.8	4"
EAW-VD9114P177F7-425AXSP04	277.8	435.4	332.7	373.6	729.6	278.7	433.6	331.9	373.3	725.2	451	17.8	3"	361	11.7	3"	541	21.6	4"
EAW-VD9114P177F7-432AXSP04	256.7	405.9	308.6	347.9	684.5	257.5	404.5	308.1	347.3	679.4	451	17.8	3"	361	11.7	3"	541	21.6	4"
EAW-VD9114P177F7-525AXSP04	307.6	477	366.5	410.8	789.8	308.3	475.8	366.1	410.3	784.5	564	16	4"	451	13	3"	676	22.5	4"
EAW-VD9114P177F7-532AXSP06	299.8	460.8	354.4	397	-	298.8	457.9	353.3	395	-	372	23.8	3"	298	15.7	3"	446	33.4	3"
EAW-VD9114P177F7-625AXSP06	342.6	515.3	400.8	446.2	-	341.4	512.5	399.1	444.3	-	451	24.9	3"	361	16.4	3"	541	31.6	4"
EAW-VD9114P177F7-632AXSP06	326.9	496.5	384.1	429.3	-	325.8	493.6	382.9	426.7	-	451	24.9	3"	361	16.4	3"	541	31.6	4"
EAW-VD9114P24716-425AXSP04	301.8	472.9	360.6	405.5	-	302	471.3	360.1	404.8	-	451	17.8	3"	361	11.7	3"	541	21.6	4"
EAW-VD9114P24716-432AXSP04	278	439	333.8	376.8	742.1	278.6	437.9	333.7	375.8	738.4	451	17.8	3"	361	11.7	3"	541	21.6	4"
EAW-VD9114P24716-525AXSP04	334.6	520.1	399	447.8	863.3	335.6	518.3	398.3	446.9	857.8	564	16	4"	451	13	3"	676	22.5	4"
EAW-VD9114P24716-532AXSP04	313.4	491	375.7	422.4	821.7	314.1	490.2	375.1	421.6	817.4	564	16	4"	451	13	3"	676	22.5	4"
EAW-VD9114P24716-625AXSP06	3																		

EAW-VD9114ZA320P7-632AXSP06	438.4	671.1	517.2	578.9	-	437.3	665.6	514.5	575.7	-	609	21.5	4"	487	17.1	3"	730	30.2	4"
EAW-VD9114Z177F-425AXSP06	334.8	514.1	396.1	443.4	-	333.1	510	392.9	439.8	-	406	24.3	3"	325	16.1	3"	487	34.2	3"
EAW-VD9114Z177F-432AXSP06	310.2	479.4	412.7	412.7	-	308.4	475.1	365.3	409.5	-	406	24.3	3"	325	16.1	3"	487	34.2	3"
EAW-VD9114Z177F-525AXSP06	372.7	565	437.7	488	-	370.9	559.5	434.5	484.4	-	507	26	3"	406	17.1	3"	609	32.1	4"
EAW-VD9114Z177F-532AXSP06	349.6	534.2	412.6	461.2	-	348.2	529.7	409.7	457.9	-	507	26	3"	406	17.1	3"	609	32.1	4"
EAW-VD9114Z177F-625AXSP06	399.8	598.4	466.9	519.2	965.9	397.8	592.7	463.6	514.9	955.8	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9114Z177F-632AXSP06	380.4	574.9	446.5	497.6	936.3	377.9	569.8	443.2	493.1	925.8	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9114Z24716-425AXSP04	350.7	549.3	419.5	471.4	918.2	350.7	545.5	418	469.6	910	609	16.4	4"	487	13.7	3"	730	23.1	4"
EAW-VD9114Z24716-432AXSP06	337.1	522.5	400.4	449.5	-	336.1	519	398.4	446.4	-	406	24.3	3"	325	16.1	3"	487	34.2	3"
EAW-VD9114Z24716-525AXSP06	407.2	619.3	479.2	534.7	-	405.8	613.8	476.2	531.4	-	507	26	3"	406	17.1	3"	609	32.1	4"
EAW-VD9114Z24716-532AXSP06	381.5	585	450.5	504.2	-	379.7	580.6	447.8	501	-	507	26	3"	406	17.1	3"	609	32.1	4"
EAW-VD9114Z24716-625AXSP06	438.1	658.1	512.5	570.3	-	436.3	652.3	509.2	565.9	-	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9114Z24716-632AXSP06	415.9	630.4	488.6	544.9	-	413.7	624.7	485.4	540.6	-	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9114Z320P5-425AXSP04	381.8	598	456.5	513.7	1002.8	381.8	594.5	454.7	511.5	993.3	609	16.4	4"	487	13.7	3"	730	23.1	4"
EAW-VD9114Z320P5-432AXSP04	349.6	552	420.3	473.9	931.5	349.9	549.4	419.2	471.6	924.6	609	16.4	4"	487	13.7	3"	730	23.1	4"
EAW-VD9114Z320P5-525AXSP04	427.6	663.4	509.7	571.7	1099.9	427.5	658.9	507.1	568.6	1089.2	755	17.6	4"	604	11.6	4"	906	21.1	(2) 4"
EAW-VD9114Z320P5-532AXSP06	415.4	638.6	491.8	550.1	-	413.2	633.3	488.5	546.3	-	507	26	3"	406	17.1	3"	609	32.1	4"
EAW-VD9114Z320P7-625AXSP06	484.2	730.4	567.4	632	-	481.8	724.1	563.3	627.3	-	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9114Z320P7-632AXSP06	455.8	694.2	536.5	598.9	-	453.7	687.3	532.7	594.6	-	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9114Z320P7-625AXSP04	389.2	610.2	465.4	524	-	389.4	607	463.9	522	1014.9	609	16.4	4"	487	13.7	3"	730	23.1	4"
EAW-VD9114Z320P7-432AXSP04	356.6	563.2	428.3	483.2	951.1	356.6	560.6	427.4	481	942.8	609	16.4	4"	487	13.7	3"	730	23.1	4"
EAW-VD9114Z320P7-525AXSP04	436.1	676.1	519.1	582.3	1123	435.5	671.8	517.5	579.5	1112.6	755	17.6	4"	604	11.6	4"	906	21.1	(2) 4"
EAW-VD9114Z320P7-532AXSP06	423.4	651.5	501.4	560.9	-	421.5	646.5	497.6	557.4	-	507	26	3"	406	17.1	3"	609	32.1	4"
EAW-VD9114Z320P7-625AXSP06	493.5	744.9	578.4	644.3	-	490.7	738	573.8	639.1	-	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9116PA177F-632AXSP06	464.2	707.5	546.4	611.1	-	462.3	701.7	542.7	605.9	-	609	23.5	4"	487	18.5	3"	730	33	4"
EAW-VD9116PA177F-425AXSP04	300.9	470.2	359.2	403.7	-	301.4	469.2	359.1	403.4	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA177F-432AXSP04	278.3	439.2	334	376.7	741.1	278.9	437.4	333.7	375.7	736.4	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA177F-525AXSP04	332.3	514.6	395.4	442.8	853.1	333	513.2	395	442.2	848.4	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA177F-532AXSP04	312.5	488.4	373.7	419.9	814.8	313.3	487.1	373.3	419.4	811.1	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA177F-625AXSP06	367.8	553.9	430.4	479.4	-	367.2	551.1	429.3	478	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD9116PA177F-632AXSP06	351.3	535.2	413.5	461.7	-	351.1	532.1	412.3	460.2	-	451	25.5	3"	361	16.8	3"	541	32.4	4"
EAW-VD9116PA24716-425AXSP04	324.8	510.1	388.2	437.8	-	326.2	508.6	388.5	437.1	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA24716-432AXSP04	300.4	474.8	360.6	406.4	-	301.4	473.3	360.6	406.4	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA24716-525AXSP04	361.1	559.7	429.4	482.2	930.3	362.1	558.5	429.2	481	926.7	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA24716-532AXSP04	337.9	528.8	404.6	454.4	886.4	339.1	527.8	404.6	454.2	881.6	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA24716-625AXSP04	385.3	592.7	457.3	511.5	974.2	386.8	590.8	457.1	510.5	968.7	676	17.2	4"	541	11.4	4"	812	24.2	4"
EAW-VD9116PA24716-632AXSP04	366.2	568.8	436.6	489.9	943.6	367.6	567.3	436.9	489.3	938.5	676	17.2	4"	541	11.4	4"	812	24.2	4"
EAW-VD9116PA320P5-425AXSP04	356.1	560.2	426.6	481.1	-	357.2	559.1	426.7	480	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA320P5-432AXSP04	327.1	517.5	393.1	443.4	-	327.9	516.8	393	443.1	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA320P5-525AXSP04	399.5	621.6	475.8	534.2	-	400.7	620.2	475.5	533.7	-	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA320P5-532AXSP04	371.6	583	444.9	500.5	-	372.8	581.5	444.7	500	-	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA320P5-625AXSP04	430.2	662.8	510.4	571.6	1093.9	431.9	661.5	510.2	570.5	1088.9	676	17.2	4"	541	11.4	4"	812	24.2	4"
EAW-VD9116PA320P5-632AXSP04	405.4	630.9	484	542.9	1050.2	407	629.2	483.5	542.3	1044.2	676	17.2	4"	541	11.4	4"	812	24.2	4"
EAW-VD9116PA320P7-425AXSP04	361.5	568.8	432.8	488.2	-	362.5	567.9	433.1	487.3	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA320P7-432AXSP04	331.6	525.3	398.6	450.3	-	332.6	524.9	398.8	449.8	-	451	18.2	3"	361	12	3"	541	22.1	4"
EAW-VD9116PA320P7-525AXSP04	405.4	631.2	482.8	542.2	-	406.5	629.7	482.5	541.7	-	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA320P7-532AXSP04	377.4	591.5	451.1	507.7	-	378.2	590.4	451.2	507.5	-	564	16.4	4"	451	13.2	3"	676	23.1	4"
EAW-VD9116PA320P7-625AXSP04	437.7	673.8	518.6	580.9	1112.5	438.5	672.1	518.1	580.2	1106.6	676	17.2	4"	541	11.4	4"	812	24.2	4"
EAW-VD9116PA320P7-632AXSP04	411.9	640.4	491	551	1066.7	412.9	638.8	490.6	550.3	1060.7	676	17.2	4"	541	11.4	4"	812	24.2	4"
EAW-VD9116P177F-425AXSP04	322.2	500.8	383.5	430.6	-	322	498.7	382.6	429.5	-	451	19.7	3"	361	13	3"	541	24.2	4"
EAW-VD9116P177F-432AXSP04	297.9	467.2	356.1	400.6	-	298.2	464.7	355.6	399.8	-	451	19.7	3"	361	13	3"	541	24.2	4"
EAW-VD9116P177F-525AXSP04	357.2	549	422.7	473	906.2	357.3	546.7	421.6	471.7	900	564	17.9	4"	451	14.3	3"	676	25.2	4"
EAW-VD9116P177F-532AXSP04	335.1	520.3	399	447.9	866.4	335.3	517.9	398.5	446.5	859.6	564	17.9	4"	451	14.3	3"	676	25.2	4"
EAW-VD9116P177F-625AXSP04	380.8	580.2	449.5	501.3	947.3	381.3	577.8	448.2	499.9	940.1	564	17.9	4"	451	14.3	3"	676	25.2	4"
EAW-VD9116P177F-632AXSP04	363	558.3	430.6	481.6	920.2	363	555.9	429.4	480.1	913.7	676	18.7	4"	541	12.4	4"	812	26.3	4"
EAW-VD9116P24716-425AXSP04	348.9	544	415.9	467.6	-	349.1	542.2	415.3	466.7	-	451	19.7	3"	361	13	3"	541	24.2	4"
EAW-VD9116P24716-432AXSP04	321.8	505.5	385	434.1	-	322.4	504.1	384.3	432.8	-	451	19.7	3"	361	13	3"	541	24.2	4"
EAW-VD9116P24716-525AXSP04	388.1	597.8	459.6	515.7	-	388.5	595.8	458.8	513.8	-	564	17.9	4"	451	14.3	3"	676	25.2	4"
EAW-VD9116P24716-532AXSP04	364	565.6	433.1	486	-	364.1	562.8	432.4	485.1	936.9	564	17.9	4"	451	14.3	3"	676	25.2	4"
EAW-VD9116P24716-625AXSP04	416.2	635	490.8	547.9	1038.6	416.3	631.8	489.6	546.5	1032.1	676	18.7	4"	541	12.4	4"	812	26.3	4"
EAW-VD9116P24716-632AXSP04	394.5	608.1	468.5	524.4	1004.5	394.8	605.8	467.4	523.1	997.9	676	18.7	4"	541	12.4	4"	812	26.3	4"
EAW-VD9116P320P5-425AXSP04	381.4	597.1	455.3	512.8	-	381.5	594.8	454.5	510.7	-	451	19.7	3"	361	13	3"	541	24.2	4"
EAW-VD9116P320P5-432AXSP04	349.9	551.4	419.4	472.4	-	350.1	548.7	418.2	471.3	-	451	19.7	3"	361	13	3"	541	24.2	4"
EAW-VD9116P320P5-525AXSP04	428.4	663.2	508.8	570.8	-	428.6	660.3	507.5	569.1	-	564	17.9	4"	451	14.3	3"	676	25.2	4"
EAW-VD9116P																			

EAW-VD9116Z177F-625AXSP06	460.5	687.1	536.3	595.6	-	457.6	680.6	531.8	590.6	-	609	26.4	4"	487	20.4	3"	730	37	4"
EAW-VD9116Z177F-632AXSP06	437.8	659.5	513.2	571	-	435.5	653.6	508.6	565.8	-	609	26.4	4"	487	20.4	3"	730	37	4"
EAW-VD9116Z24716-425AXSP04	407.3	631.7	484.4	543.2	-	406.5	627.3	481.8	540.2	-	609	18.3	4"	487	15	3"	730	25.7	4"
EAW-VD9116Z24716-432AXSP04	375	587.2	448.3	503.7	984.9	374.7	583.4	446.3	501.2	976.4	609	18.3	4"	487	15	3"	730	25.7	4"
EAW-VD9116Z24716-525AXSP04	451.5	693.5	534.8	599	1143.3	450.8	689.4	532.5	595.4	1133.4	755	19.5	4"	604	12.8	4"	906	23.8	(2) 4"
EAW-VD9116Z24716-532AXSP04	422.4	654.9	502.6	563.7	1087	421.4	650.2	500.5	560.4	1077.2	755	19.5	4"	604	12.8	4"	906	23.8	(2) 4"
EAW-VD9116Z24716-625AXSP04	487.3	741.1	574.9	640.9	1207.4	486.1	735.5	571.3	637.7	1195.5	913	17.3	(2) 4"	730	13.8	4"	1096	24.3	(2) 4"
EAW-VD9116Z24716-632AXSP06	478.8	723.3	561.5	625.3	-	475.6	716.7	557.1	621.2	-	609	26.4	4"	487	20.4	3"	730	37	4"
EAW-VD9116Z320P5-425AXSP04	442	688.9	526.3	592.1	-	441.1	683.7	524.3	588.6	-	609	18.3	4"	487	15	3"	730	25.7	4"
EAW-VD9116Z320P5-432AXSP04	405.7	635.4	485	545.8	-	404.9	632.3	482.8	543	-	609	18.3	4"	487	15	3"	730	25.7	4"
EAW-VD9116Z320P5-525AXSP04	495.8	763.6	587	658.2	-	494.8	758.3	584	653.7	1249.6	755	19.5	4"	604	12.8	4"	906	23.8	(2) 4"
EAW-VD9116Z320P5-532AXSP04	460.2	714.4	548.1	614.6	1190.8	458.9	709.8	544.7	611.5	1179.2	755	19.5	4"	604	12.8	4"	906	23.8	(2) 4"
EAW-VD9116Z320P5-625AXSP04	539.5	822.1	636.1	710.7	1343.5	537.9	816.3	632.5	705.7	1330.7	913	17.3	(2) 4"	730	13.8	4"	1096	24.3	(2) 4"
EAW-VD9116Z320P5-632AXSP04	506.7	780.4	601.3	672.7	1287.4	505.5	774.9	598.1	668.9	1273.1	913	17.3	(2) 4"	730	13.8	4"	1096	24.3	(2) 4"
EAW-VD9116Z320P7-425AXSP04	450.6	702	536.7	604	-	449.9	698.1	534.9	600.6	-	609	18.3	4"	487	15	3"	730	25.7	4"
EAW-VD9116Z320P7-432AXSP04	413.4	648.3	494.4	556.5	-	412.9	644.1	492.3	553.8	-	609	18.3	4"	487	15	3"	730	25.7	4"
EAW-VD9116Z320P7-525AXSP04	505.7	778.2	598.8	670.6	-	504.1	773.2	596	667.3	-	755	19.5	4"	604	12.8	4"	906	23.8	(2) 4"
EAW-VD9116Z320P7-532AXSP04	468.9	728.7	558.7	626.6	1213.8	467.9	724.4	555.5	623.9	1202.6	755	19.5	4"	604	12.8	4"	906	23.8	(2) 4"
EAW-VD9116Z320P7-625AXSP04	549.9	838.4	648.3	723.6	1370.6	548.5	831.8	645.1	719.8	1358.1	913	17.3	(2) 4"	730	13.8	4"	1096	24.3	(2) 4"
EAW-VD9116Z320P7-632AXSP04	516.7	795.3	612.4	686.3	1312.6	514.8	790	609.3	681.6	1300.1	913	17.3	(2) 4"	730	13.8	4"	1096	24.3	(2) 4"
EAW-VD9118PA177F-425AXSP04	341.7	532.5	407	457.3	-	342.2	530.5	406.9	457	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD9118PA177F-432AXSP04	316.7	496.8	378.5	426.2	-	317	494.7	378.4	425.1	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD9118PA177F-525AXSP04	378.7	582.2	448.3	501.9	-	378.8	580.6	447.8	500.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA177F-532AXSP04	355.9	552.8	423.3	475.5	920.6	356.1	550.5	422.8	474.1	915.1	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA177F-625AXSP04	402.9	613.8	475	530	1002.9	403.5	611.5	474.5	529.3	996.8	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA177F-632AXSP04	384.4	592.3	456.2	510.4	976	385	589.7	455.6	509.6	970.5	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA24716-425AXSP04	369.6	576.8	440.9	496	-	369.8	576	440.3	495.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD9118PA24716-432AXSP04	341.6	537.1	408.6	460.6	-	341.9	535.5	408.6	459.9	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD9118PA24716-525AXSP04	410.3	633.4	487	545.8	-	411.3	631.9	486.7	544.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA24716-532AXSP04	385	598.8	458.4	514.7	-	385.6	597.5	458.3	514.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA24716-625AXSP04	439.3	670.3	518.2	578.7	1098.6	440.2	668.1	517.9	577.5	1093.8	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA24716-632AXSP04	417.4	643.5	495	555.3	1064.4	418.2	641.8	494.5	553.7	1058.5	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA320P5-425AXSP02	355.1	592	439.1	502	1020.3	360.8	593.7	442.6	504.8	1018.1	902	9.3	(2) 4"	721	8.4	4"	1082	13.1	(2) 4"
EAW-VD9118PA320P5-432AXSP04	371.8	586.8	445.6	502.5	-	372.2	584.8	445	501.5	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD9118PA320P5-525AXSP04	454.2	703.6	538.6	604.9	-	454.6	700.8	538.5	604.3	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA320P5-532AXSP04	422.9	660.3	504.2	567.1	-	423.4	657.5	503.9	565.5	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA320P5-625AXSP04	489.2	749.7	578.5	646.8	-	490.3	748.2	578.2	646.4	-	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA320P5-632AXSP04	462.3	714	548	614.7	-	462.5	712.1	547.5	613.9	-	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA320P7-425AXSP02	360.1	600.8	445.6	509.7	1036.4	366.2	602.8	449.4	512.4	1032.8	902	9.3	(2) 4"	721	8.4	4"	1082	13.1	(2) 4"
EAW-VD9118PA320P7-432AXSP04	376.9	594.5	451.9	509.8	-	377.6	594	452.1	509.2	-	451	19.9	3"	361	13.1	3"	541	24.5	4"
EAW-VD9118PA320P7-525AXSP04	460.8	714.4	547.7	614	-	461.2	711.6	546.4	613.4	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA320P7-532AXSP04	428.7	670	511.3	575.2	-	429.5	667.6	511.3	574	-	564	18.1	4"	451	14.4	3"	676	25.5	4"
EAW-VD9118PA320P7-625AXSP04	497	762.2	587.8	657.4	-	497.8	760.2	587.1	656.5	-	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118PA320P7-632AXSP04	468.9	724.8	556	623.8	-	469.2	723	555.5	623	-	676	18.9	4"	541	12.5	4"	812	26.6	4"
EAW-VD9118P177F-425AXSP04	365.8	567	434.5	487.7	-	365.5	563.7	432.7	485.6	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD9118P177F-432AXSP04	338.2	528.3	403.8	454.1	-	338.2	525.5	402.3	452.3	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD9118P177F-525AXSP04	405.6	621	479.1	535.2	-	405.1	617.6	477.2	533.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9118P177F-532AXSP04	381.6	588.9	452.6	507.2	-	381	586.1	450.5	504.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9118P177F-625AXSP04	433.8	656	509.1	567.7	1068.2	433.1	652.5	507.7	565.3	1060.1	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9118P177F-632AXSP04	412.8	631.5	488.1	544.9	1037.8	412.7	628.7	485.9	543.2	1030.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9118P24716-425AXSP02	351.9	577.5	432	491.8	986.7	356.5	578.1	434.4	493.2	983.3	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9118P24716-432AXSP04	365.5	571.8	436.2	491.2	-	365.6	570.2	435.8	489.7	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD9118P24716-525AXSP04	440.8	676.4	521.2	583.7	-	440.6	674	519.3	581.5	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9118P24716-532AXSP04	413.2	639.3	490.6	550.4	-	413.2	637.1	489	548.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9118P24716-625AXSP04	472.9	717.2	556	620.6	-	472.3	714.4	553.9	618.1	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9118P24716-632AXSP04	448.8	688	530.3	593.5	-	449	684.3	529	591.1	1125.5	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9118P320P5-425AXSP02	386	633.5	473.8	539.8	1085.7	390.6	633.9	476	541.2	1081.3	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9118P320P5-432AXSP02	352.3	583.7	434.2	495.6	1005.3	356.8	584.6	436.4	497.3	1002	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9118P320P5-525AXSP02	486	749.4	576.2	646.2	-	486.2	746.2	574.6	643.2	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9118P320P5-532AXSP04	452.2	703.4	538.6	604.1	-	452	699.5	536.5	602.6	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9118P320P5-625AXSP04	525.8	801.5	619.6	692.3	-	525.1	797.2	617.1	689.4	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9118P320P5-632AXSP04	495.3	761.7	586.8	656.6	-	495.4	758.2	584.2	654.5	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9118P320P7-425AXSP02	392.2	643.8	481.1	548.3	1102.6	396.7	644.6	483.7	550.2	1098.8	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9118P320P7-432AXSP02	358.1	593.5	441	503.7	1023.1	362.9	594.5	443.7	505.6	101									

EAW-VD9118ZJ24716-532AXSP04	480.1	740.1	569.1	638.2	1226.2	478.8	735.7	566.7	634.4	1215.1	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9118ZJ24716-625AXSP04	554.2	837.9	651.1	725.7	1361.4	552.8	831.5	647	720.2	1348.1	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9118ZJ24716-632AXSP04	525.4	802	620	692.8	1314.4	523.5	795.9	616.2	688.3	1301	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9118ZJ320P5-425AXSP04	501.8	778.8	596.3	669.6	-	500.7	772.9	593.9	665.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9118ZJ320P5-432AXSP04	460.6	719.9	548.9	617.4	-	459.1	713.8	546.3	614.2	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9118ZJ320P5-525AXSP04	563.1	863.9	665.5	745	-	560.9	856.7	661	739.7	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9118ZJ320P5-532AXSP04	523.2	808.6	620.8	695.9	-	521.6	802.1	616.9	691.3	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9118ZJ320P5-625AXSP04	613.9	929.6	720.6	803.9	1516.8	611	921.8	716.5	798.1	1500.5	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9118ZJ320P5-632AXSP04	576.3	882.8	680.6	761.2	1452	574.7	875.4	676.9	755.8	1435.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9118ZJ320P7-425AXSP04	511.6	794.8	608.1	683	-	509.8	789.2	604.9	679.2	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9118ZJ320P7-432AXSP04	469.4	733.2	560.6	629.6	-	468	728.5	557	626.6	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9118ZJ320P7-525AXSP04	573.5	880.5	677.9	759	-	571.5	873.6	674.6	754	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9118ZJ320P7-532AXSP04	533.1	824.9	632.8	709.6	-	531.9	818.7	629.2	705.3	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9118ZJ320P7-625AXSP04	624.8	948	734.5	819.6	-	622.3	940.5	729.7	813	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9118ZJ320P7-632AXSP04	587.7	899.7	694.2	776.6	1480.5	585.4	892.4	689.6	771.3	1466.3	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120PA177F7-425AXSP04	382.4	594.5	455.5	511.6	-	382.9	592.2	454.5	510.4	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD9120PA177F7-432AXSP04	354.8	555	423.1	476.3	-	354.7	552.7	422.1	475	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD9120PA177F7-525AXSP04	424.1	649.7	501.2	560.2	-	424.1	647.9	499.8	559.4	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9120PA177F7-532AXSP04	398.9	617.1	473.5	530.9	-	399.1	614.4	472.2	529.3	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9120PA177F7-625AXSP04	452.1	684.6	530.7	592.1	1116.9	452.1	682	530.1	590.5	1110.2	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA177F7-632AXSP04	431.8	660.8	510	570.5	1087.2	431.7	658	508.5	568.7	1081	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA24716-425AXSP02	368.1	605.2	451.7	514.6	1034.5	373.3	605.9	455	517.1	1031.3	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9120PA24716-432AXSP04	382.4	599.1	456.9	514.9	-	382.7	597.2	456.3	513	-	451	21.6	3"	361	14.2	3"	541	26.9	4"
EAW-VD9120PA24716-525AXSP04	459.7	707.9	544.6	609.3	-	460	705.2	543.3	608.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9120PA24716-532AXSP04	430.9	668.5	512	574.9	-	431.5	666	511.9	573.5	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9120PA24716-625AXSP04	492.4	747.7	579	646.5	-	492.6	745.2	577.9	645.2	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA24716-632AXSP04	468.2	719.1	553.5	619.8	-	468.3	716.2	552.9	618	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA320P5-425AXSP02	405	664.1	496.8	566.3	1139.4	409.8	665.8	500.1	568.7	1136.9	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9120PA320P5-432AXSP02	370	613.2	455.7	520.9	1056.4	374.9	614.2	458.9	522.8	1054.4	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9120PA320P5-525AXSP02	453.4	739	553.7	628.7	1252.6	459	740.2	557	632	1249.7	1127	10.8	(2) 4"	902	7.1	(2) 4"	1352	15.2	(2) 4"
EAW-VD9120PA320P5-532AXSP04	473.5	737.4	563.4	633.5	-	474	734.2	562.9	631.7	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9120PA320P5-625AXSP04	548.5	837.5	646.6	722.8	-	548.9	834.7	645.3	721.3	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA320P5-632AXSP04	517.1	796.9	612.9	687.3	-	517.3	794.7	612.2	685.2	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA320P7-425AXSP02	410.9	674	504.8	575.1	1157.4	416	676	507.8	577.1	1153.3	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9120PA320P7-432AXSP02	375.2	622.1	462.9	528.7	1072.8	380.5	623.6	466	530.5	1069.6	902	10.2	(2) 4"	721	9	4"	1082	14.3	(2) 4"
EAW-VD9120PA320P7-525AXSP02	459.7	750.1	562.6	639	1272.3	466.2	751.3	565.9	641.2	1269.3	1127	10.8	(2) 4"	902	7.1	(2) 4"	1352	15.2	(2) 4"
EAW-VD9120PA320P7-532AXSP04	480	747	571.3	642.6	-	480.8	745.5	571.2	641.1	-	564	19.8	4"	451	15.5	3"	676	27.9	4"
EAW-VD9120PA320P7-625AXSP04	556.4	851.5	657	734.6	-	557.3	848.1	655.3	732.5	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120PA320P7-632AXSP04	524.5	809	621.9	697.5	-	524.8	806.8	621.2	695.5	-	676	20.6	4"	541	13.6	4"	812	29	4"
EAW-VD9120ZA177F7-425AXSP04	448.3	692.6	531.9	596.2	-	447.4	687.9	529.2	598	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA177F7-432AXSP04	414.6	645.2	493.4	555	-	413.6	641.2	491.3	551.4	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA177F7-532AXSP04	497.4	758.1	586.3	655.3	1245.1	495.3	752.8	583.1	650.7	1233.2	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA177F7-532AXSP04	466.1	717.6	552.4	618.2	1187.7	464.9	712.4	549.3	614.6	1177.2	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA177F7-625AXSP04	534.4	807.1	627.7	699.4	1310.6	533.2	801.3	624	694.4	1296.9	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA177F7-632AXSP04	507.7	775.2	599.9	670	1269.5	506.8	769.5	596.3	665.9	1257.1	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA24716-425AXSP04	487.8	755.8	579.4	650.3	-	486.8	751.5	577.2	646.5	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA24716-432AXSP04	450	702.6	536.3	603	-	449.4	698.8	534.5	600.7	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA24716-525AXSP04	542	830	640.3	715.3	-	541	823.7	637.3	711.8	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA24716-532AXSP04	507.1	782.5	601.5	674	-	506.5	777.8	598.9	670.8	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA24716-625AXSP04	585.5	885.3	687.1	766.2	1441.6	583.4	880.1	683.9	761.6	1429.8	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA24716-632AXSP04	554.5	848.1	654.6	731.8	1391.6	553.1	841.3	651.3	727.9	1380.6	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA320P5-425AXSP04	531	825.5	631.6	709.8	-	529.5	820.1	629.7	706.2	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA320P5-432AXSP04	487.3	762.4	581.6	654	-	486.1	758.1	578.6	651.3	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA320P5-525AXSP04	594.9	914.9	704.5	789.2	-	593.4	908.6	700.7	783.6	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA320P5-532AXSP04	553.3	856.4	657	737.2	-	552.4	850.7	653.8	733.3	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA320P5-625AXSP04	648.5	985.2	762.6	851.3	-	646.6	977.3	758.5	845.4	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA320P5-632AXSP04	610.3	934.5	720.1	806	-	608.6	927.7	717.1	801.2	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA320P7-425AXSP02	480.9	789.1	589.8	671.6	1348.9	485.9	789.3	591.7	672	1340.9	1217	11.2	(2) 4"	974	7.4	(2) 4"	1461	15.7	(2) 4"
EAW-VD9120ZA320P7-432AXSP04	496	776.9	592.7	667.3	-	495	771.6	590.6	663.8	-	609	20.2	4"	487	16.3	3"	730	28.4	4"
EAW-VD9120ZA320P7-525AXSP04	605.8	931.1	716.5	802.8	-	604.7	925.1	714.2	798.7	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA320P7-532AXSP04	562.7	871.9	668.4	751.4	-	562	866.4	666.5	746.5	-	755	21.4	4"	604	14.1	4"	906	26.4	(2) 4"
EAW-VD9120ZA320P7-625AXSP04	659.7	1001.6	775.9	866.2	-	658	995.1	771.9	860.5	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9120ZA320P7-632AXSP04	620.4	952.1	733.3	820.9	-	619	945.7	729.5	816.4	-	913	19.3	(2) 4"	730	15.1	4"	1096	27	(2) 4"
EAW-VD9151MA177F7-425AXSP16	-</																		

EAW-VD91S3MA24716-525AXSP12	80.8	123.7	95.5	106.8	-	80.7	123	95	106.3	-	113	22.8	1-1/2"	90	15	1-1/2"	135	32	1-1/2"
EAW-VD91S3MA24716-532AXSP12	75.7	117	89.8	100.6	-	75.7	116.3	89.4	100.2	-	113	22.8	1-1/2"	90	15	1-1/2"	135	32	1-1/2"
EAW-VD91S3MA320P5-425AXSP08	74.7	119.3	90.3	102.2	201.8	75	118.9	90.4	102	200.5	146	14	2"	117	11.3	1-1/2"	176	19.6	2"
EAW-VD91S3MA320P5-432AXSP12	72.6	113.7	86.8	97.5	-	72.5	113.1	86.3	97.2	-	90	21.7	1-1/2"	72	14.3	1-1/2"	108	30.4	1-1/2"
EAW-VD91S3MA320P5-525AXSP12	89	136.6	105.3	117.9	-	88.7	135.7	104.7	117.2	-	113	22.8	1-1/2"	90	15	1-1/2"	135	32	1-1/2"
EAW-VD91S3MA320P5-532AXSP12	82.8	128	98.3	110.3	-	82.5	127.2	97.8	109.7	-	113	22.8	1-1/2"	90	15	1-1/2"	135	32	1-1/2"
EAW-VD91S3MA320P7-425AXSP08	75.9	121.4	92	104	205.6	76.4	121	92.1	103.8	204.3	146	14	2"	117	11.3	1-1/2"	176	19.6	2"
EAW-VD91S3MA320P7-432AXSP12	73.9	115.8	88.3	99.5	-	73.8	115.2	88.1	99	-	90	21.7	1-1/2"	72	14.3	1-1/2"	108	30.4	1-1/2"
EAW-VD91S3MA320P7-525AXSP12	90.5	139.1	107	119.8	-	90.3	138.3	106.6	119.3	-	113	22.8	1-1/2"	90	15	1-1/2"	135	32	1-1/2"
EAW-VD91S3MA320P7-532AXSP12	84.2	130.5	100	112.2	-	84.1	129.7	99.5	111.7	-	113	22.8	1-1/2"	90	15	1-1/2"	135	32	1-1/2"
EAW-VD91S4MA177F7-425AXSP08	87.1	136	104	116.8	226.6	87.2	135.1	103.7	116.4	224.8	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA177F7-432AXSP08	80.5	126.6	96.6	108.7	212.6	80.5	125.9	96.2	108.2	210.9	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA177F7-525AXSP08	95.8	148.1	113.9	127.5	244	95.8	147.1	113.5	127.1	242.1	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA177F7-532AXSP08	89.8	140.1	107.2	120.5	232.9	89.8	139.3	106.9	120	231	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA24716-425AXSP08	94.8	147.9	113.1	127.2	-	94.8	147.4	112.9	126.7	-	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA24716-432AXSP08	87.4	137.7	104.8	118.1	231.7	87.5	137.1	104.6	117.8	230.1	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA24716-525AXSP08	104.6	161.8	124.4	139.3	267.6	104.7	160.8	123.9	138.9	265.6	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA24716-532AXSP08	97.7	152.7	116.8	131.2	254.4	97.7	151.8	116.5	130.8	252.5	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA320P5-425AXSP08	103.5	161.8	123.6	139	-	103.5	161.1	123.2	138.4	-	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA320P5-432AXSP08	94.9	149.4	113.8	128.3	-	94.9	148.9	113.5	127.8	-	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA320P5-525AXSP08	115.3	178.5	137	153.6	296.5	115.3	177.6	136.6	153.1	294.1	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA320P5-532AXSP08	106.9	167.3	127.7	143.6	279.6	107	166.2	127.4	143.2	277.4	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA320P7-425AXSP08	105.2	165	125.7	141.4	-	105.3	164.1	125.5	141.1	-	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA320P7-432AXSP08	96.6	152.4	115.8	130.6	-	96.7	151.7	115.6	130.2	-	146	17.4	2"	117	13.6	1-1/2"	176	24.4	2"
EAW-VD91S4MA320P7-525AXSP08	117.1	181.5	139.3	156.4	-	117.2	180.7	138.9	155.7	299.4	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S4MA320P7-532AXSP08	108.8	170.2	130	146.3	284.7	108.8	169.2	129.8	145.7	282.6	180	18.3	2"	144	12.1	2"	216	25.8	2"
EAW-VD91S5MA177F7-425AXSP08	111.2	171.5	131.7	147.9	-	110.8	170.4	131.1	146.9	-	146	20.8	2"	117	15.9	1-1/2"	176	29.2	2"
EAW-VD91S5MA177F7-432AXSP08	102.8	159.9	122.3	137.6	-	102.5	159	121.8	136.7	-	146	20.8	2"	117	15.9	1-1/2"	176	29.2	2"
EAW-VD91S5MA177F7-525AXSP08	122.4	186.9	144.3	161.3	-	122.1	185.6	143.5	160.4	-	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA177F7-532AXSP08	114.9	177	136	152.5	292.6	114.5	175.6	135.3	151.7	290.3	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA24716-425AXSP08	120.7	187	143.4	160.9	-	120.5	186	142.9	160.3	-	146	20.8	2"	117	15.9	1-1/2"	176	29.2	2"
EAW-VD91S5MA24716-432AXSP08	111.4	174	132.8	149.6	-	111.4	172.9	132.5	148.9	-	146	20.8	2"	117	15.9	1-1/2"	176	29.2	2"
EAW-VD91S5MA24716-525AXSP08	133.5	204.2	157.4	176.2	-	133.1	203	156.8	175.4	-	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA24716-532AXSP08	124.9	192.6	148	166.1	-	124.6	191.5	147.4	165.1	-	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA320P5-425AXSP06	126.5	198.5	151.4	170.4	-	126.5	197.8	151.2	170	-	192	17.4	2"	153	11.4	2"	230	24.4	2"
EAW-VD91S5MA320P5-432AXSP08	120.8	189.2	144.3	162.3	-	120.6	187.8	143.6	161.6	-	146	20.8	2"	117	15.9	1-1/2"	176	29.2	2"
EAW-VD91S5MA320P5-525AXSP08	146.7	225.4	173.5	194.4	-	146.4	223.9	172.6	193.4	-	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA320P5-532AXSP08	136.3	211.1	161.8	181.6	-	136.1	209.8	161.1	180.8	-	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA320P7-425AXSP06	128.8	202.4	154	173.6	-	128.9	201.3	153.8	173	-	192	17.4	2"	153	11.4	2"	230	24.4	2"
EAW-VD91S5MA320P7-432AXSP08	123	192.6	146.8	165.1	-	122.8	191.4	146.2	164.6	-	146	20.8	2"	117	15.9	1-1/2"	176	29.2	2"
EAW-VD91S5MA320P7-525AXSP08	149.1	229.6	176.6	197.6	-	148.9	228.2	175.8	196.7	-	180	21.8	2"	144	14.3	2"	216	30.6	2"
EAW-VD91S5MA320P7-532AXSP08	138.8	214.8	164.9	185	-	138.5	213.6	164.2	183.9	-	180	21.8	2"	144	14.3	2"	216	30.6	2"



Evapco EAW Line Thermal Performance in USGPM - 30% Ethylene Glycol as Process Fluid

Range °F	10	10	15	15	9	10	10	15	15	9	First	First	First	Second	Second	Second	Third	Third	Third
Approach °F	5	10	10	12	18	5	10	10	12	18	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow
Dry Bulb Temperature °F	77	77	77	77	77	95	95	95	95	95	GPM	PSI	Inlet	GPM	PSI	Inlet	GPM	PSI	Inlet
EAW-DD1504X017G7-525AXSP08	370.6	605.4	455.3	516.4	1033.6	375.2	603.5	455.9	515.6	1021.7	654	16.3	4"	523	10.7	4"	784	22.8	4"
EAW-DD1504X017G7-625AXSP12	440.4	684.7	523.6	588	-	439.9	678.4	521.2	584	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD1504X017G7-632AXSP12	412.0	646.1	492.2	553.7	-	411.3	640.3	489.5	549.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD1508X017G7-525AXSP04	735.5	1205	905.6	1027.6	2061.3	746.2	1201.3	907	1026.1	2037.7	1319	18.1	4"	1055	11.4	4"	1582	20.9	6"
EAW-DD1508X017G7-625AXSP06	875.2	1362	1042.5	1170.9	-	874.4	1351.2	1036.2	1161.3	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD1508X017G7-632AXSP06	818.3	1284.5	977.9	1102.1	-	818.5	1273	972.6	1093.5	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD1512X017G7-525AXSP04	1192.4	1877.1	1426.8	1610	-	1191.6	1861.2	1420	1598.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD1512X017G7-625AXSP04	1304.6	2034.5	1554.2	1746	-	1305.6	2015.9	1545	1731.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD1512X017G7-632AXSP04	1219.0	1915.3	1459.6	1642.6	-	1219.5	1901.1	1451.9	1629.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3351X030M3-525AXSP12	336.3	526.3	401.4	451.8	-	335.7	520.7	398.5	447.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030M3-625AXSP12	371.8	574.6	441.2	494.4	-	371	568.2	437.6	489.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M3-632AXSP12	349.2	544.5	416.2	467.7	-	348.7	538.4	413.4	462.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M4-525AXSP12	336.3	526.3	401.4	451.8	-	335.7	520.7	398.5	447.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030M4-625AXSP12	371.8	574.6	441.2	494.4	-	371	568.2	437.6	489.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M4-632AXSP12	349.2	544.5	416.2	467.7	-	348.7	538.4	413.4	462.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M5-525AXSP12	336.3	526.3	401.4	451.8	-	335.7	520.7	398.5	447.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030M5-625AXSP12	371.8	574.6	441.2	494.4	-	371	568.2	437.6	489.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M5-632AXSP12	349.2	544.5	416.2	467.7	-	348.7	538.4	413.4	462.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M9-525AXSP12	336.3	526.3	401.4	451.8	-	335.7	520.7	398.5	447.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030M9-625AXSP12	371.8	574.6	441.2	494.4	-	371	568.2	437.6	489.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030M9-632AXSP12	349.2	544.5	416.2	467.7	-	348.7	538.4	413.4	462.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N3-525AXSP12	324.9	507.5	387.5	435.3	-	324	501.6	384.4	431.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030N3-625AXSP12	359.4	554.7	426.3	477.5	-	358.6	547.8	422.2	472	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N3-632AXSP12	336.8	525.1	401.8	450.6	871	336	518.7	398.2	446.3	856.9	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N4-525AXSP12	324.9	507.5	387.5	435.3	-	324	501.6	384.4	431.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030N4-625AXSP12	359.4	554.7	426.3	477.5	-	358.6	547.8	422.2	472	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N4-632AXSP12	336.8	525.1	401.8	450.6	871	336	518.7	398.2	446.3	856.9	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N5-525AXSP12	324.9	507.5	387.5	435.3	-	324	501.6	384.4	431.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030N5-625AXSP12	359.4	554.7	426.3	477.5	-	358.6	547.8	422.2	472	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N5-632AXSP12	336.8	525.1	401.8	450.6	871	336	518.7	398.2	446.3	856.9	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N9-525AXSP12	324.9	507.5	387.5	435.3	-	324	501.6	384.4	431.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030N9-625AXSP12	359.4	554.7	426.3	477.5	-	358.6	547.8	422.2	472	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030N9-632AXSP12	336.8	525.1	401.8	450.6	871	336	518.7	398.2	446.3	856.9	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030Q3-525AXSP12	324.9	507.5	387.5	435.3	-	324	501.6	384.4	431.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030Q3-625AXSP12	359.4	554.7	426.3	477.5	-	358.6	547.8	422.2	472	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030Q3-632AXSP12	336.8	525.1	401.8	450.6	871	336	518.7	398.2	446.3	856.9	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030T3-525AXSP12	336.3	526.3	401.4	451.8	-	335.7	520.7	398.5	447.4	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030T3-625AXSP12	371.8	574.6	441.2	494.4	-	371	568.2	437.6	489.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030T3-632AXSP12	349.2	544.5	416.2	467.7	-	348.7	538.4	413.4	462.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X3-525AXSP12	327.3	511.6	390.5	439.4	-	327.3	506.9	388.3	435.2	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030X3-525AXSP16	334.9	516.7	396.7	444.7	-	333	510.5	392.6	439.8	-	316	30.8	4"	252	20.4	4"	379	43.2	4"
EAW-DD3351X030X3-625AXSP12	361.5	557.3	428.2	479.7	-	360.6	551.7	425.2	475.4	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X3-625AXSP16	371.4	565.9	437.3	488.2	-	369.3	558.7	432.3	482.4	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X030X3-632AXSP12	339.7	529.9	405.4	454.8	879.3	339.4	524.1	402.2	450.9	865	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X3-632AXSP16	350.0	537.3	413.4	462.8	-	347.7	530.5	409.5	457.4	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X030X4-525AXSP12	327.3	511.6	390.5	439.4	-	327.3	506.9	388.3	435.2	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030X4-625AXSP12	361.5	557.3	428.2	479.7	-	360.6	551.7	425.2	475.4	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X4-632AXSP12	339.7	529.9	405.4	454.8	879.3	339.4	524.1	402.2	450.9	865	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X5-525AXSP12	327.3	511.6	390.5	439.4	-	327.3	506.9	388.3	435.2	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030X5-625AXSP12	361.5	557.3	428.2	479.7	-	360.6	551.7	425.2	475.4	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X5-632AXSP12	339.7	529.9	405.4	454.8	879.3	339.4	524.1	402.2	450.9	865	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X9-525AXSP12	327.3	511.6	390.5	439.4	-	327.3	506.9	388.3	435.2	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X030X9-625AXSP12	361.5	557.3	428.2	479.7	-	360.6	551.7	425.2	475.4	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030X9-632AXSP12	339.7	529.9	405.4	454.8	879.3	339.4	524.1	402.2	450.9	865	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X030Y3-625AXSP16	334.9	516.7	396.7	444.7	-	333	510.5	392.6	439.8	-	316	30.8	4"	252	20.4	4"	379	43.2	4"
EAW-DD3351X030Y3-625AXSP16	371.4	565.9	437.3	488.2	-	369.3	558.7	432.3	482.4	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X030Y3-625AXSP16	350.0	537.3	413.4	462.8	-	347.7	530.5	409.5	457.4	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X030Y3-625AXSP16	371.4	565.9	437.3	488.2	-	369.3	558.7	432.3	482.4	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X030Y3-625AXSP16	350.0	537.3	413.4	462.8	-	347.7	530.5	409.5	457.4	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X037M3-525AXSP12	351.8	552	420.9	473.3	-	351.4	546.4	418	469	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X037M3-625AXSP12	390.1	603.3	463.2	519.3	-	389.5	597.5	459.5	514.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X037M3-632AXSP12	365.9	571.1	436.4	490	-	365.1	565.7	433.1	486	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X037M4-525AXSP12	351.8	552	420.9	473.3	-	351.4	546.4	418	469	-	4								

EAW-DD3351X1037X5-525AXSP12	343.6	538.4	410.9	461.9	-	343.2	533	408.2	457.7	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1037X5-625AXSP12	380.6	587.9	451.7	506.3	-	379.8	582.1	448	501.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1037X5-632AXSP12	357.3	557	426	478.1	-	356.5	551.8	422.8	474.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1037X9-525AXSP12	343.6	538.4	410.9	461.9	-	343.2	533	408.2	457.7	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1037X9-625AXSP12	380.6	587.9	451.7	506.3	-	379.8	582.1	448	501.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1037X9-632AXSP12	357.3	557	426	478.1	-	356.5	551.8	422.8	474.3	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1037Y3-525AXSP12	343.6	538.4	410.9	461.9	-	343.2	533	408.2	457.7	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1037Y3-625AXSP16	391.3	597.1	460.8	514.7	-	388.6	588.9	455.6	508.7	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X1037Y3-632AXSP16	367.1	565.6	434.6	486.7	-	364.9	558.7	430.6	481.2	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X1045M3-525AXSP12	370.5	582.2	443.6	499.3	-	370.6	576.8	440.5	495.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045M3-625AXSP12	411.3	637.5	488.6	548.2	-	410.9	631.8	485.8	543.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M3-632AXSP12	385.3	603	459.9	516.8	-	385	597.1	457	513.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M4-525AXSP12	370.5	582.2	443.6	499.3	-	370.6	576.8	440.5	495.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045M4-621AXSP08	373.4	607.3	457.3	519.2	1020.8	379.1	604.6	458.5	518.3	1007.9	789	16.7	4"	631	11	4"	947	23.4	4"
EAW-DD3351X1045M4-625AXSP12	411.3	637.5	488.6	548.2	-	410.9	631.8	485.8	543.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M4-632AXSP12	385.3	603	459.9	516.8	-	385	597.1	457	513.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M5-525AXSP12	370.5	582.2	443.6	499.3	-	370.6	576.8	440.5	495.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045M5-625AXSP12	411.3	637.5	488.6	548.2	-	410.9	631.8	485.8	543.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M5-632AXSP12	385.3	603	459.9	516.8	-	385	597.1	457	513.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M9-525AXSP12	370.5	582.2	443.6	499.3	-	370.6	576.8	440.5	495.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045M9-625AXSP12	411.3	637.5	488.6	548.2	-	410.9	631.8	485.8	543.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045M9-632AXSP12	385.3	603	459.9	516.8	-	385	597.1	457	513.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N3-525AXSP12	358.9	562.8	428.8	482.3	-	358.4	556.9	425.8	478.5	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045N3-625AXSP12	398.3	617.3	473.7	531.2	-	398	610.3	469.7	525.7	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N3-632AXSP12	372.8	582.4	444.7	500.2	-	372.5	576.7	441.9	495.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N4-525AXSP12	358.9	562.8	428.8	482.3	-	358.4	556.9	425.8	478.5	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045N4-625AXSP12	398.3	617.3	473.7	531.2	-	398	610.3	469.7	525.7	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N4-632AXSP12	372.8	582.4	444.7	500.2	-	372.5	576.7	441.9	495.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N5-525AXSP12	358.9	562.8	428.8	482.3	-	358.4	556.9	425.8	478.5	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045N5-625AXSP12	398.3	617.3	473.7	531.2	-	398	610.3	469.7	525.7	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N5-632AXSP12	372.8	582.4	444.7	500.2	-	372.5	576.7	441.9	495.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N9-525AXSP12	358.9	562.8	428.8	482.3	-	358.4	556.9	425.8	478.5	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045N9-625AXSP12	398.3	617.3	473.7	531.2	-	398	610.3	469.7	525.7	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045N9-632AXSP12	372.8	582.4	444.7	500.2	-	372.5	576.7	441.9	495.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045Q3-525AXSP12	358.9	562.8	428.8	482.3	-	358.4	556.9	425.8	478.5	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045Q3-625AXSP12	398.3	617.3	473.7	531.2	-	398	610.3	469.7	525.7	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045Q3-632AXSP12	372.8	582.4	444.7	500.2	-	372.5	576.7	441.9	495.2	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045T3-525AXSP12	370.5	582.2	443.6	499.3	-	370.6	576.8	440.5	495.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045T3-625AXSP12	411.3	637.5	488.6	548.2	-	410.9	631.8	485.8	543.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045T3-632AXSP12	385.3	603	459.9	516.8	-	385	597.1	457	513.1	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X3-525AXSP12	360.5	565.3	430.7	484.5	-	359.6	559.8	428	480.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045X3-625AXSP12	399.5	618.5	474.5	532.1	-	398.9	612.6	471.4	526.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X3-625AXSP16	410.9	628.3	484.1	541.1	-	408.3	620.6	479.5	534.9	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X1045X3-632AXSP12	374.3	584.8	446.5	502.3	-	373.7	578.8	443.4	497.6	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X3-632AXSP16	384.7	594.1	455.7	510.7	-	382.6	587	451.6	505.1	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X1045X4-525AXSP12	360.5	565.3	430.7	484.5	-	359.6	559.8	428	480.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045X4-625AXSP12	399.5	618.5	474.5	532.1	-	398.9	612.6	471.4	526.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X4-632AXSP12	374.3	584.8	446.5	502.3	-	373.7	578.8	443.4	497.6	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X5-525AXSP12	360.5	565.3	430.7	484.5	-	359.6	559.8	428	480.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045X5-625AXSP12	399.5	618.5	474.5	532.1	-	398.9	612.6	471.4	526.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X5-632AXSP12	374.3	584.8	446.5	502.3	-	373.7	578.8	443.4	497.6	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X9-525AXSP12	360.5	565.3	430.7	484.5	-	359.6	559.8	428	480.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045X9-625AXSP12	399.5	618.5	474.5	532.1	-	398.9	612.6	471.4	526.9	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045X9-632AXSP12	374.3	584.8	446.5	502.3	-	373.7	578.8	443.4	497.6	-	530	23.6	4"	424	15.6	4"	636	33	4"
EAW-DD3351X1045Y3-525AXSP12	360.5	565.3	430.7	484.5	-	359.6	559.8	428	480.3	-	428	23.4	4"	343	15.5	4"	514	32.7	4"
EAW-DD3351X1045Y3-625AXSP16	410.9	628.3	484.1	541.1	-	408.3	620.6	479.5	534.9	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3351X1045Y3-632AXSP16	384.7	594.1	455.7	510.7	-	382.6	587	451.6	505.1	-	394	31	4"	316	20.5	4"	473	43.4	4"
EAW-DD3352X1030M3-525AXSP06	678.3	1061.9	809.3	910.5	-	677.9	1050.3	804.5	903	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352X1030M3-625AXSP06	739.3	1143.3	877.4	983.4	-	738.8	1130.6	871.5	974.7	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352X1030M3-632AXSP06	693.9	1083	828.5	929.8	-	693.1	1072.3	821.9	921.8	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352X1030M4-525AXSP06	678.3	1061.9	809.3	910.5	-	677.9	1050.3	804.5	903	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352X1030M4-625AXSP06	739.3	1143.3	877.4	983.4	-	738.8	1130.6	871.5	974.7	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352X1030M4-632AXSP06	693.9	1083	828.5	929.8	-	693.1	1072.3	821.9	921.8	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352X1030M5-525AXSP06	678.3	1061.9	809.3	910.5	-	677.9	1050.3	804.5	903	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352X1030M5-625AXSP06	739.3	1143.3	877.4	983.4	-	738.8	1130.6	871.5	974.7	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352X1030M5-632AXSP06	693.9	1083	828.5	929.8															

EAW-DD3352XL030X9-632AXSP06	675.20	1054	805.8	905.5	1751.8	674.6	1042.5	799.6	896.5	1723.4	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL030Y3-525AXSP08	680.50	1048.2	805.8	902.8	-	676.5	1035.4	797.2	892.6	-	654	29.4	4"	523	19.5	4"	784	41.2	4"
EAW-DD3352XL030Y3-625AXSP08	739.70	1127.4	870.9	972.5	-	735.6	1113.3	862.2	961	-	789	29.9	4"	631	19.7	4"	947	41.9	4"
EAW-DD3352XL030Y3-632AXSP08	696.70	1071.6	823.2	922.9	-	692.3	1058.2	815.3	910.9	-	789	29.9	4"	631	19.7	4"	947	41.9	4"
EAW-DD3352XL037M3-525AXSP06	710.80	1113.8	848.7	955.5	-	709.8	1102.2	842.8	946.6	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037M3-625AXSP06	775.60	1201.8	921	1032.8	-	774.4	1188.8	915.1	1024.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M3-632AXSP06	727.10	1135.8	867.3	975.6	-	726.7	1125.1	862.2	966.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M4-525AXSP06	710.80	1113.8	848.7	955.5	-	709.8	1102.2	842.8	946.6	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037M4-625AXSP06	775.60	1201.8	921	1032.8	-	774.4	1188.8	915.1	1024.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M4-632AXSP06	727.10	1135.8	867.3	975.6	-	726.7	1125.1	862.2	966.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M5-525AXSP06	710.80	1113.8	848.7	955.5	-	709.8	1102.2	842.8	946.6	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037M5-625AXSP06	775.60	1201.8	921	1032.8	-	774.4	1188.8	915.1	1024.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M5-632AXSP06	727.10	1135.8	867.3	975.6	-	726.7	1125.1	862.2	966.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M9-525AXSP06	710.80	1113.8	848.7	955.5	-	709.8	1102.2	842.8	946.6	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037M9-625AXSP06	775.60	1201.8	921	1032.8	-	774.4	1188.8	915.1	1024.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037M9-632AXSP06	727.10	1135.8	867.3	975.6	-	726.7	1125.1	862.2	966.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N3-525AXSP06	700.60	1097	837.6	941.3	-	700	1086.2	831	933.2	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037N3-625AXSP06	766.90	1186.1	910.5	1020.9	-	764.8	1173.5	903.7	1011.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N3-632AXSP06	716.80	1120.5	856.2	961.4	-	715.9	1109.2	849.2	952.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N4-525AXSP06	700.60	1097	837.6	941.3	-	700	1086.2	831	933.2	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037N4-625AXSP06	766.90	1186.1	910.5	1020.9	-	764.8	1173.5	903.7	1011.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N4-632AXSP06	716.80	1120.5	856.2	961.4	-	715.9	1109.2	849.2	952.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N5-525AXSP06	700.60	1097	837.6	941.3	-	700	1086.2	831	933.2	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037N5-625AXSP06	766.90	1186.1	910.5	1020.9	-	764.8	1173.5	903.7	1011.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N5-632AXSP06	716.80	1120.5	856.2	961.4	-	715.9	1109.2	849.2	952.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N9-525AXSP06	700.60	1097	837.6	941.3	-	700	1086.2	831	933.2	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037N9-625AXSP06	766.90	1186.1	910.5	1020.9	-	764.8	1173.5	903.7	1011.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037N9-632AXSP06	716.80	1120.5	856.2	961.4	-	715.9	1109.2	849.2	952.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037Q3-525AXSP06	700.60	1097	837.6	941.3	-	700	1086.2	831	933.2	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037Q3-625AXSP06	766.90	1186.1	910.5	1020.9	-	764.8	1173.5	903.7	1011.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037Q3-632AXSP06	716.80	1120.5	856.2	961.4	-	715.9	1109.2	849.2	952.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037T3-525AXSP06	710.80	1113.8	848.7	955.5	-	709.8	1102.2	842.8	946.6	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037T3-625AXSP06	775.60	1201.8	921	1032.8	-	774.4	1188.8	915.1	1024.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037T3-632AXSP06	727.10	1135.8	867.3	975.6	-	726.7	1125.1	862.2	966.1	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037Y3-625AXSP06	694.20	1086.3	828.5	932.4	-	693.1	1075.1	822.8	923.8	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037X3-525AXSP08	713.80	-	847.1	949.7	-	710	1090.5	838.3	937.8	-	654	29.4	4"	523	19.5	4"	784	41.2	4"
EAW-DD3352XL037X3-625AXSP06	756.60	1171.2	898.2	1007	-	755.2	1158.3	892.3	998.2	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X3-625AXSP08	779.10	1189.6	917.6	1025.2	-	773.9	1174.7	908.7	1013.2	-	789	29.9	4"	631	19.7	4"	947	41.9	4"
EAW-DD3352XL037X3-632AXSP06	710.00	1109.2	846.6	952	-	709.7	1097.5	841.8	942.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X3-632AXSP08	731.90	1126.5	865.2	969.2	-	727.6	1112.8	857.2	958.3	-	789	29.9	4"	631	19.7	4"	947	41.9	4"
EAW-DD3352XL037X4-525AXSP06	694.20	1086.3	828.5	932.4	-	693.1	1075.1	822.8	923.8	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037X4-625AXSP06	756.60	1171.2	898.2	1007	-	755.2	1158.3	892.3	998.2	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X4-632AXSP06	710.00	1109.2	846.6	952	-	709.7	1097.5	841.8	942.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X5-525AXSP06	694.20	1086.3	828.5	932.4	-	693.1	1075.1	822.8	923.8	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037X5-625AXSP06	756.60	1171.2	898.2	1007	-	755.2	1158.3	892.3	998.2	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X5-632AXSP06	710.00	1109.2	846.6	952	-	709.7	1097.5	841.8	942.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X9-525AXSP06	694.20	1086.3	828.5	932.4	-	693.1	1075.1	822.8	923.8	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL037X9-625AXSP06	756.60	1171.2	898.2	1007	-	755.2	1158.3	892.3	998.2	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037X9-632AXSP06	710.00	1109.2	846.6	952	-	709.7	1097.5	841.8	942.9	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL037Y3-525AXSP08	713.80	-	847.1	949.7	-	710	1090.5	838.3	937.8	-	654	29.4	4"	523	19.5	4"	784	41.2	4"
EAW-DD3352XL037Y3-625AXSP08	779.10	1189.6	917.6	1025.2	-	773.9	1174.7	908.7	1013.2	-	789	29.9	4"	631	19.7	4"	947	41.9	4"
EAW-DD3352XL037Y3-632AXSP08	731.90	1126.5	865.2	969.2	-	727.6	1112.8	857.2	958.3	-	789	29.9	4"	631	19.7	4"	947	41.9	4"
EAW-DD3352XL045M3-525AXSP06	748.70	1174.8	894.7	1006.5	-	747.4	1163.9	889.5	999.9	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL045M3-625AXSP06	817.60	1269.8	971.4	1091.7	-	817	1256.9	966	1081.6	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M3-632AXSP06	765.50	1199	913.9	1028.8	-	765	1187.5	909.6	1020	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M4-525AXSP06	748.70	1174.8	894.7	1006.5	-	747.4	1163.9	889.5	999.9	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL045M4-621AXSP06	812.80	1258	965.2	1082.5	-	811.8	1248.2	959.4	1073.7	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M4-625AXSP06	817.60	1269.8	971.4	1091.7	-	817	1256.9	966	1081.6	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M4-632AXSP06	765.50	1199	913.9	1028.8	-	765	1187.5	909.6	1020	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M5-525AXSP06	748.70	1174.8	894.7	1006.5	-	747.4	1163.9	889.5	999.9	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL045M5-625AXSP06	817.60	1269.8	971.4	1091.7	-	817	1256.9	966	1081.6	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M5-632AXSP06	765.50	1199	913.9	1028.8	-	765	1187.5	909.6	1020	-	1060	23.9	4"	848	15.8	4"	1271	33.5	4"
EAW-DD3352XL045M9-525AXSP06	748.70	1174.8	894.7	1006.5	-	747.4	1163.9	889.5	999.9	-	879	23.1	4"	703	15.2	4"	1055	32.4	4"
EAW-DD3352XL045M9-625AXSP06	817.60	1269.8	971.4	1091.7	-	817	1256.9	966	1081.6	-	1060	23.9	4"	848	15.8	4			

EAW-DD3353XL030M3-625AXSP04	1102.30	1706	1310.4	1469	-	1101.9	1689.4	1299.9	1454.2	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030M3-632AXSP04	1034.20	1615.3	1235	1388.5	-	1033.2	1599.6	1227.2	1374.5	2647.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030M3-632AXSP04	1010.70	1583.6	1208.1	1359.5	-	1010.4	1566.6	1199.2	1346.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030M4-625AXSP04	1102.30	1706	1310.4	1469	-	1101.9	1689.4	1299.9	1454.2	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030M4-625AXSP04	1034.20	1615.3	1235	1388.5	-	1033.2	1599.6	1227.2	1374.5	2647.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030M9-525AXSP04	1010.70	1583.6	1208.1	1359.5	-	1010.4	1566.6	1199.2	1346.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030M9-525AXSP04	1102.30	1706	1310.4	1469	-	1101.9	1689.4	1299.9	1454.2	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030M9-632AXSP04	1034.20	1615.3	1235	1388.5	-	1033.2	1599.6	1227.2	1374.5	2647.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030N3-525AXSP04	976.30	1526.8	1164.5	1309.8	-	975	1511.2	1156.7	1298	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030N3-632AXSP04	1065.60	1646.9	1264.5	1419	-	1063.7	1628.8	1254.5	1402.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030N4-525AXSP04	997.50	1557.7	1190.7	1338.1	2589.8	995.6	1541.3	1182.1	1325.4	2548.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030N4-632AXSP04	976.30	1526.8	1164.5	1309.8	-	975	1511.2	1156.7	1298	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030N5-625AXSP04	1065.60	1646.9	1264.5	1419	-	1063.7	1628.8	1254.5	1402.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030N5-625AXSP04	997.50	1557.7	1190.7	1338.1	2589.8	995.6	1541.3	1182.1	1325.4	2548.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030N9-525AXSP04	976.30	1526.8	1164.5	1309.8	-	975	1511.2	1156.7	1298	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030N9-525AXSP04	1065.60	1646.9	1264.5	1419	-	1063.7	1628.8	1254.5	1402.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030N9-632AXSP04	997.50	1557.7	1190.7	1338.1	2589.8	995.6	1541.3	1182.1	1325.4	2548.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030Q3-525AXSP04	976.30	1526.8	1164.5	1309.8	-	975	1511.2	1156.7	1298	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030Q3-525AXSP04	1065.60	1646.9	1264.5	1419	-	1063.7	1628.8	1254.5	1402.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030Q3-632AXSP04	997.50	1557.7	1190.7	1338.1	2589.8	995.6	1541.3	1182.1	1325.4	2548.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030T3-525AXSP04	1010.70	1583.6	1208.1	1359.5	-	1010.4	1566.6	1199.2	1346.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030T3-625AXSP04	1102.30	1706	1310.4	1469	-	1101.9	1689.4	1299.9	1454.2	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030T3-632AXSP04	1034.20	1615.3	1235	1388.5	-	1033.2	1599.6	1227.2	1374.5	2647.4	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X3-525AXSP04	985.20	1541.4	1175.3	1322.1	-	983.4	1525.1	1168.6	1311.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030X3-625AXSP04	1071.80	1656.8	1271.9	1425.4	-	1071.2	1640.6	1263.4	1412.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X3-625AXSP06	1122.20	1701.9	1317.2	1470.4	-	1114.2	1680.4	1302.2	1451	-	1060	33.7	4"	848	22.3	4"	1271	47.3	4"
EAW-DD3353XL030X3-632AXSP04	1006.30	1572.1	1201.3	1350.2	2614.3	1005.6	1557.3	1194.1	1339	2575.3	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X3-632AXSP06	1056.40	1618.4	1245.9	1394.4	-	1047.9	1595.9	1232	1376.1	-	1060	33.7	4"	848	22.3	4"	1271	47.3	4"
EAW-DD3353XL030X4-525AXSP04	985.20	1541.4	1175.3	1322.1	-	983.4	1525.1	1168.6	1311.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030X4-625AXSP04	1071.80	1656.8	1271.9	1425.4	-	1071.2	1640.6	1263.4	1412.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X4-625AXSP04	1006.30	1572.1	1201.3	1350.2	2614.3	1005.6	1557.3	1194.1	1339	2575.3	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X5-525AXSP04	985.20	1541.4	1175.3	1322.1	-	983.4	1525.1	1168.6	1311.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030X5-625AXSP04	1071.80	1656.8	1271.9	1425.4	-	1071.2	1640.6	1263.4	1412.9	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X5-632AXSP04	1006.30	1572.1	1201.3	1350.2	2614.3	1005.6	1557.3	1194.1	1339	2575.3	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030X9-525AXSP04	985.20	1541.4	1175.3	1322.1	-	983.4	1525.1	1168.6	1311.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030X9-525AXSP04	1122.20	1701.9	1317.2	1470.4	-	1114.2	1680.4	1302.2	1451	-	1060	33.7	4"	848	22.3	4"	1271	47.3	4"
EAW-DD3353XL030X9-632AXSP04	1006.30	1572.1	1201.3	1350.2	2614.3	1005.6	1557.3	1194.1	1339	2575.3	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL030Y3-525AXSP04	985.20	1541.4	1175.3	1322.1	-	983.4	1525.1	1168.6	1311.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL030Y3-625AXSP06	1056.40	1618.4	1245.9	1394.4	-	1047.9	1595.9	1232	1376.1	-	1060	33.7	4"	848	22.3	4"	1271	47.3	4"
EAW-DD3353XL037M3-525AXSP04	1059.10	1661	1264.8	1424.4	-	1057.7	1643.8	1258.1	1411.2	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037M3-625AXSP04	1156.40	1793.2	1373.5	1542.8	-	1154.8	1773.9	1364.9	1527.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M3-632AXSP04	1083.50	1696.3	1294.9	1454.5	-	1083.2	1678.2	1285.3	1442.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M4-525AXSP04	1059.10	1661	1264.8	1424.4	-	1057.7	1643.8	1258.1	1411.2	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037M4-625AXSP04	1156.40	1793.2	1373.5	1542.8	-	1154.8	1773.9	1364.9	1527.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M4-632AXSP04	1083.50	1696.3	1294.9	1454.5	-	1083.2	1678.2	1285.3	1442.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M5-525AXSP04	1059.10	1661	1264.8	1424.4	-	1057.7	1643.8	1258.1	1411.2	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037M5-625AXSP04	1156.40	1793.2	1373.5	1542.8	-	1154.8	1773.9	1364.9	1527.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M5-632AXSP04	1083.50	1696.3	1294.9	1454.5	-	1083.2	1678.2	1285.3	1442.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M9-525AXSP04	1059.10	1661	1264.8	1424.4	-	1057.7	1643.8	1258.1	1411.2	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037M9-625AXSP04	1156.40	1793.2	1373.5	1542.8	-	1154.8	1773.9	1364.9	1527.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037M9-632AXSP04	1083.50	1696.3	1294.9	1454.5	-	1083.2	1678.2	1285.3	1442.7	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N3-525AXSP04	1043.80	1635.9	1248.3	1405.5	-	1043.2	1620	1238.7	1391.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037N3-625AXSP04	1143.40	1772.1	1357.9	1522.8	-	1140.5	1751.2	1347.8	1508.4	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N3-632AXSP04	1069.90	1671.1	1276.2	1435.5	-	1067.1	1654.6	1268	1420.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N4-525AXSP04	1043.80	1635.9	1248.3	1405.5	-	1043.2	1620	1238.7	1391.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037N4-625AXSP04	1143.40	1772.1	1357.9	1522.8	-	1140.5	1751.2	1347.8	1508.4	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N4-632AXSP04	1069.90	1671.1	1276.2	1435.5	-	1067.1	1654.6	1268	1420.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N5-525AXSP04	1043.80	1635.9	1248.3	1405.5	-	1043.2	1620	1238.7	1391.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037N5-625AXSP04	1143.40	1772.1	1357.9	1522.8	-	1140.5	1751.2	1347.8	1508.4	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N5-632AXSP04	1069.90	1671.1	1276.2	1435.5	-	1067.1	1654.6	1268	1420.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL037N9-525AXSP04	1043.80	1635.9	1248.3	1405.5	-	1043.2	1620	1238.7	1391.3	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL037N9-632AXSP04	1143.40	1772.1	1357.9	1522.8	-	1140.5	1751.2	1347.8	1508.4	-	1589	21.8	6"	1271	17.4	4"	19		

Note: "-" indicates flow rate is outside of unit capability

EAW-DD3353XL045M5-632AXSP04	1140.60	1788	1364.2	1533.6	-	1140	1773.5	1355.9	1523	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045M9-525AXSP04	1115.40	1751.7	1333.2	1502.6	-	1115.5	1735.6	1327.8	1490.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045M9-625AXSP04	1218.80	1894.5	1450.7	1628.2	-	1218.2	1875.3	1440.5	1613.4	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045M9-632AXSP04	1140.60	1788	1364.2	1533.6	-	1140	1773.5	1355.9	1523	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N3-525AXSP04	1078.60	1693.4	1290.6	1451.5	-	1077	1678	1281.5	1440.1	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045N3-625AXSP04	1182.20	1834.9	1404.5	1575.7	-	1180.1	1814.3	1395	1561.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N3-632AXSP04	1103.60	1729.6	1319.3	1484.7	-	1103.1	1710.7	1309.4	1470.1	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N4-525AXSP04	1078.60	1693.4	1290.6	1451.5	-	1077	1678	1281.5	1440.1	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045N4-625AXSP04	1182.20	1834.9	1404.5	1575.7	-	1180.1	1814.3	1395	1561.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N4-632AXSP04	1103.60	1729.6	1319.3	1484.7	-	1103.1	1710.7	1309.4	1470.1	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N5-525AXSP04	1078.60	1693.4	1290.6	1451.5	-	1077	1678	1281.5	1440.1	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045N5-625AXSP04	1182.20	1834.9	1404.5	1575.7	-	1180.1	1814.3	1395	1561.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N5-632AXSP04	1103.60	1729.6	1319.3	1484.7	-	1103.1	1710.7	1309.4	1470.1	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N9-525AXSP04	1078.60	1693.4	1290.6	1451.5	-	1077	1678	1281.5	1440.1	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045N9-625AXSP04	1182.20	1834.9	1404.5	1575.7	-	1180.1	1814.3	1395	1561.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045N9-632AXSP04	1103.60	1729.6	1319.3	1484.7	-	1103.1	1710.7	1309.4	1470.1	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045Q3-525AXSP04	1078.60	1693.4	1290.6	1451.5	-	1077	1678	1281.5	1440.1	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045Q3-625AXSP04	1182.20	1834.9	1404.5	1575.7	-	1180.1	1814.3	1395	1561.8	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045Q3-632AXSP04	1103.60	1729.6	1319.3	1484.7	-	1103.1	1710.7	1309.4	1470.1	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045T3-525AXSP04	1115.40	1751.7	1333.2	1502.6	-	1115.5	1735.6	1327.8	1490.5	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045T3-625AXSP04	1218.80	1894.5	1450.7	1628.2	-	1218.2	1875.3	1440.5	1613.4	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045T3-632AXSP04	1140.60	1788	1364.2	1533.6	-	1140	1773.5	1355.9	1523	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X3-525AXSP04	1083.20	1701.1	1296.3	1458	-	1082.5	1684.4	1288.1	1447.6	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045X3-625AXSP04	1184.10	1838.2	1408.9	1580.7	-	1182.7	1820.9	1398.1	1565.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X3-632AXSP04	1108.00	1736.9	1324.6	1490.8	-	1108.4	1719.2	1315.7	1477.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X4-525AXSP04	1083.20	1701.1	1296.3	1458	-	1082.5	1684.4	1288.1	1447.6	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045X4-625AXSP04	1184.10	1838.2	1408.9	1580.7	-	1182.7	1820.9	1398.1	1565.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X4-632AXSP04	1108.00	1736.9	1324.6	1490.8	-	1108.4	1719.2	1315.7	1477.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X5-525AXSP04	1083.20	1701.1	1296.3	1458	-	1082.5	1684.4	1288.1	1447.6	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045X5-625AXSP04	1184.10	1838.2	1408.9	1580.7	-	1182.7	1820.9	1398.1	1565.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X5-632AXSP04	1108.00	1736.9	1324.6	1490.8	-	1108.4	1719.2	1315.7	1477.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X9-525AXSP04	1083.20	1701.1	1296.3	1458	-	1082.5	1684.4	1288.1	1447.6	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045X9-625AXSP04	1184.10	1838.2	1408.9	1580.7	-	1182.7	1820.9	1398.1	1565.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045X9-632AXSP04	1108.00	1736.9	1324.6	1490.8	-	1108.4	1719.2	1315.7	1477.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045Y3-525AXSP04	1083.20	1701.1	1296.3	1458	-	1082.5	1684.4	1288.1	1447.6	-	1319	24.7	4"	1055	16.3	4"	1582	30.1	6"
EAW-DD3353XL045Y3-625AXSP04	1184.10	1838.2	1408.9	1580.7	-	1182.7	1820.9	1398.1	1565.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-DD3353XL045Y3-632AXSP04	1108.00	1736.9	1324.6	1490.8	-	1108.4	1719.2	1315.7	1477.3	-	1589	21.8	6"	1271	17.4	4"	1907	30.6	6"
EAW-FD1551PB370C2-425AXSP16	37.00	61.9	46	52.5	107.3	37.9	62.3	46.6	52.9	106.9	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C2-432AXSP16	34.30	58	43	49.2	101.2	35.2	58.3	43.5	49.6	100.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C2-525AXSP16	40.00	66.8	49.8	56.8	114.3	41.1	67.2	50.4	57.4	114.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C2-532AXSP16	37.80	63.9	47.3	54.3	110.2	38.9	64.2	47.9	54.7	109.9	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C2-625AXSP16	41.70	69.5	51.8	59.1	117.5	43.1	69.9	52.6	59.6	117.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C2-632AXSP16	40.10	67.7	50.2	57.4	115.7	41.4	68.1	50.8	57.9	115.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C4-425AXSP16	37.00	61.9	46	52.5	107.3	37.9	62.3	46.6	52.9	106.9	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C4-432AXSP16	34.30	58	43	49.2	101.2	35.2	58.3	43.5	49.6	100.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C4-525AXSP16	40.00	66.8	49.8	56.8	114.3	41.1	67.2	50.4	57.4	114.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C4-532AXSP16	37.80	63.9	47.3	54.3	110.2	38.9	64.2	47.9	54.7	109.9	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C4-625AXSP16	41.70	69.5	51.8	59.1	117.5	43.1	69.9	52.6	59.6	117.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C4-632AXSP16	40.10	67.7	50.2	57.4	115.7	41.4	68.1	50.8	57.9	115.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C5-425AXSP16	37.00	61.9	46	52.5	107.3	37.9	62.3	46.6	52.9	106.9	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C5-432AXSP16	34.30	58	43	49.2	101.2	35.2	58.3	43.5	49.6	100.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C5-525AXSP16	40.00	66.8	49.8	56.8	114.3	41.1	67.2	50.4	57.4	114.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C5-532AXSP16	37.80	63.9	47.3	54.3	110.2	38.9	64.2	47.9	54.7	109.9	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C5-625AXSP16	41.70	69.5	51.8	59.1	117.5	43.1	69.9	52.6	59.6	117.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C5-632AXSP16	40.10	67.7	50.2	57.4	115.7	41.4	68.1	50.8	57.9	115.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C8-425AXSP16	37.00	61.9	46	52.5	107.3	37.9	62.3	46.6	52.9	106.9	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C8-432AXSP16	34.30	58	43	49.2	101.2	35.2	58.3	43.5	49.6	100.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370C8-525AXSP16	40.00	66.8	49.8	56.8	114.3	41.1	67.2	50.4	57.4	114.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C8-532AXSP16	37.80	63.9	47.3	54.3	110.2	38.9	64.2	47.9	54.7	109.9	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD1551PB370C8-625AXSP16	41.70	69.5	51.8	59.1	117.5	43.1	69.9	52.6	59.6	117.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370C8-632AXSP16	40.10	67.7	50.2	57.4	115.7	41.4	68.1	50.8	57.9	115.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD1551PB370K2-425AXSP16	36.10	60.5	45.1	51.4	104.8	37	60.7	45.5	51.7	104.3	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370K2-432AXSP16	33.30	56.5	41.8	48	98.6	34.2	56.8	42.3	48.2	98.1	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD1551PB370K2-525AXSP16	39.50	65.9	49.																

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1PB400C9-625AXSP16	41.70	69.5	51.8	59.1	117.5	43.1	69.9	52.6	59.6	117.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400C9-632AXSP16	40.10	67.7	50.2	57.4	115.7	41.4	68.1	50.8	57.9	115.2	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400K3-425AXSP16	36.10	60.5	45.1	51.4	104.8	37	60.7	45.5	51.7	104.3	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB400K3-432AXSP16	33.30	56.5	41.8	48	98.6	34.2	56.8	42.3	48.2	98.1	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB400K3-525AXSP16	39.50	65.9	49.1	56.2	112.8	40.5	66.2	49.7	56.4	112.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB400K3-532AXSP16	37.00	62.6	46.4	53.1	108.1	38	62.9	46.9	53.5	107.5	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB400K3-625AXSP16	41.70	69.3	51.6	58.9	117.2	42.8	69.6	52.3	59.2	116.6	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400K3-632AXSP16	39.60	66.9	49.5	56.6	114.2	40.8	67.1	50.1	57.1	113.6	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400K9-425AXSP16	36.10	60.5	45.1	51.4	104.8	37	60.7	45.5	51.7	104.3	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB400K9-432AXSP16	33.30	56.5	41.8	48	98.6	34.2	56.8	42.3	48.2	98.1	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB400K9-525AXSP16	39.50	65.9	49.1	56.2	112.8	40.5	66.2	49.7	56.4	112.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB400K9-532AXSP16	37.00	62.6	46.4	53.1	108.1	38	62.9	46.9	53.5	107.5	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB400K9-625AXSP16	41.70	69.3	51.6	58.9	117.2	42.8	69.6	52.3	59.2	116.6	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400K9-632AXSP16	39.60	66.9	49.5	56.6	114.2	40.8	67.1	50.1	57.1	113.6	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400R3-425AXSP16	36.50	61.1	45.5	51.9	105.9	37.4	61.4	46	52.2	105.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB400R3-432AXSP16	33.70	57.1	42.3	48.5	99.8	34.6	57.5	42.8	48.8	99.3	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB400R3-525AXSP16	39.90	66.5	49.6	56.6	113.9	41	66.8	50.2	57	113.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB400R3-532AXSP16	37.40	63.3	46.9	53.7	109.2	38.5	63.5	47.4	54.1	108.7	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB400R3-625AXSP16	42.00	69.9	52.1	59.4	118.3	43.2	70.2	52.8	59.9	117.8	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB400R3-632AXSP16	40.10	67.5	50	57.2	115.2	41.2	67.8	50.6	57.6	114.7	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550B3-425AXSP16	38.20	63.8	47.5	54.2	110.9	39.2	64.4	48.2	54.7	110.7	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550B3-432AXSP16	35.50	60.1	44.5	50.9	104.9	36.5	60.5	45.2	51.4	104.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550B3-525AXSP16	-	-	-	-	-	-	-	-	-	-	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550B3-532AXSP16	-	-	-	-	-	40.1	66.3	49.5	56.4	113.4	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550B3-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550B3-632AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C2-425AXSP16	41.00	68.5	50.9	58.1	-	42.1	68.9	51.5	58.6	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C2-432AXSP16	37.90	63.9	47.3	54.2	112	38.8	64.3	47.9	54.6	111.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C2-525AXSP16	44.70	74.3	55.5	63.1	127.6	45.9	74.8	56.3	63.8	127.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C2-532AXSP16	42.00	70.6	52.5	60	122.3	43.1	71.1	53.2	60.5	122.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C2-632AXSP16	-	-	-	-	-	46.1	75.7	56.6	64.4	128.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C3-425AXSP16	41.00	68.5	50.9	58.1	-	42.1	68.9	51.5	58.6	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C3-432AXSP16	37.90	63.9	47.3	54.2	112	38.8	64.3	47.9	54.6	111.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C3-525AXSP16	44.70	74.3	55.5	63.1	127.6	45.9	74.8	56.3	63.8	127.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C3-532AXSP16	42.00	70.6	52.5	60	122.3	43.1	71.1	53.2	60.5	122.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C3-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C3-632AXSP16	-	-	-	-	-	46.1	75.7	56.6	64.4	128.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C4-425AXSP16	41.00	68.5	50.9	58.1	-	42.1	68.9	51.5	58.6	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C4-432AXSP16	37.90	63.9	47.3	54.2	112	38.8	64.3	47.9	54.6	111.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C4-525AXSP16	44.70	74.3	55.5	63.1	127.6	45.9	74.8	56.3	63.8	127.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C4-532AXSP16	42.00	70.6	52.5	60	122.3	43.1	71.1	53.2	60.5	122.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C4-632AXSP16	-	-	-	-	-	46.1	75.7	56.6	64.4	128.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C5-425AXSP16	41.00	68.5	50.9	58.1	-	42.1	68.9	51.5	58.6	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C5-432AXSP16	37.90	63.9	47.3	54.2	112	38.8	64.3	47.9	54.6	111.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C5-525AXSP16	44.70	74.3	55.5	63.1	127.6	45.9	74.8	56.3	63.8	127.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C5-532AXSP16	42.00	70.6	52.5	60	122.3	43.1	71.1	53.2	60.5	122.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C5-632AXSP16	-	-	-	-	-	46.1	75.7	56.6	64.4	128.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C8-425AXSP16	41.00	68.5	50.9	58.1	-	42.1	68.9	51.5	58.6	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C8-432AXSP16	37.90	63.9	47.3	54.2	112	38.8	64.3	47.9	54.6	111.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C8-525AXSP16	44.70	74.3	55.5	63.1	127.6	45.9	74.8	56.3	63.8	127.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C8-532AXSP16	42.00	70.6	52.5	60	122.3	43.1	71.1	53.2	60.5	122.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C8-632AXSP16	-	-	-	-	-	46.1	75.7	56.6	64.4	128.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C9-425AXSP16	41.00	68.5	50.9	58.1	-	42.1	68.9	51.5	58.6	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C9-432AXSP16	37.90	63.9	47.3	54.2	112	38.8	64.3	47.9	54.6	111.5	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550C9-525AXSP16	44.70	74.3	55.5	63.1	127.6	45.9	74.8	56.3	63.8	127.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C9-532AXSP16	42.00	70.6	52.5	60	122.3	43.1	71.1	53.2	60.5	122.1	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550C9-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550C9-632AXSP16	-	-	-	-	-	46.1	75.7	56.6	64.4	128.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550K2-425AXSP16	39.40	65.8	49	55.9	-	40.3	66.2	49.5	56.3	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550K2-432AXSP16	36.30	61.4	45.5	52.1	107.4	37.3	61.8	46	52.4	107	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550K2-525AXSP16	43.10	71.8	53.6	61.1	123.1	44.3	72.2	54.2	61.5	122.7	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550K2-532AXSP16	40.40	68.1	50.5	57.8	117.9	41.5	68.4	51.1	58.3	117.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB550K2-625AXSP16	45.50	75.5	56.4	64.3	128.1	46.7	75.9	57.1	64.8	127.5	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550K2-632AXSP16	43.20	72.7	54	61.7	124.5	44.5	73.1	54.7	62.2	124	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB550K3-425AXSP16	39.40	65.8	49	55.9	-	40.3	66.2	49.5	56.3	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550K3-432AXSP16	36.30	61.4	45.5	52.1	107.4	37.3	61.8	46	52.4	107	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB550K3-5																			

EAW-FD15S1PB750K2-432AXSP16	38.30	64.6	47.9	54.8	-	39.3	65	48.4	55.2	112.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K2-525AXSP16	45.20	75.2	56.2	64	129.4	46.4	75.7	57	64.5	129	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K2-532AXSP16	42.40	71.4	53.1	60.6	123.7	43.6	71.9	53.8	61.1	123.4	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K2-625AXSP16	47.70	79	59.1	67.4	134.3	49	79.4	59.9	67.9	133.9	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K2-632AXSP16	45.30	76.1	56.5	64.7	130.5	46.6	76.6	57.4	65.3	130.1	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K3-425AXSP16	41.50	69.3	51.5	58.7	-	42.6	69.7	52.1	59.3	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K3-432AXSP16	38.30	64.6	47.9	54.8	-	39.3	65	48.4	55.2	112.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K3-525AXSP16	45.20	75.2	56.2	64	129.4	46.4	75.7	57	64.5	129	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K3-532AXSP16	42.40	71.4	53.1	60.6	123.7	43.6	71.9	53.8	61.1	123.4	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K3-625AXSP16	47.70	79	59.1	67.4	134.3	49	79.4	59.9	67.9	133.9	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K3-632AXSP16	45.30	76.1	56.5	64.7	130.5	46.6	76.6	57.4	65.3	130.1	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K4-425AXSP16	41.50	69.3	51.5	58.7	-	42.6	69.7	52.1	59.3	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K4-432AXSP16	38.30	64.6	47.9	54.8	-	39.3	65	48.4	55.2	112.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K4-525AXSP16	45.20	75.2	56.2	64	129.4	46.4	75.7	57	64.5	129	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K4-532AXSP16	42.40	71.4	53.1	60.6	123.7	43.6	71.9	53.8	61.1	123.4	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K4-625AXSP16	47.70	79	59.1	67.4	134.3	49	79.4	59.9	67.9	133.9	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K4-632AXSP16	45.30	76.1	56.5	64.7	130.5	46.6	76.6	57.4	65.3	130.1	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K5-425AXSP16	41.50	69.3	51.5	58.7	-	42.6	69.7	52.1	59.3	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K5-432AXSP16	38.30	64.6	47.9	54.8	-	39.3	65	48.4	55.2	112.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K5-525AXSP16	45.20	75.2	56.2	64	129.4	46.4	75.7	57	64.5	129	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K5-532AXSP16	42.40	71.4	53.1	60.6	123.7	43.6	71.9	53.8	61.1	123.4	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K5-625AXSP16	47.70	79	59.1	67.4	134.3	49	79.4	59.9	67.9	133.9	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K5-632AXSP16	45.30	76.1	56.5	64.7	130.5	46.6	76.6	57.4	65.3	130.1	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K9-425AXSP16	41.50	69.3	51.5	58.7	-	42.6	69.7	52.1	59.3	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K9-432AXSP16	38.30	64.6	47.9	54.8	-	39.3	65	48.4	55.2	112.8	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750K9-525AXSP16	45.20	75.2	56.2	64	129.4	46.4	75.7	57	64.5	129	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K9-532AXSP16	42.40	71.4	53.1	60.6	123.7	43.6	71.9	53.8	61.1	123.4	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750K9-625AXSP16	47.70	79	59.1	67.4	134.3	49	79.4	59.9	67.9	133.9	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750K9-632AXSP16	45.30	76.1	56.5	64.7	130.5	46.6	76.6	57.4	65.3	130.1	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750R3-425AXSP16	40.60	67.9	50.4	57.6	-	41.7	68.4	51.1	58.1	-	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750R3-432AXSP16	37.50	63.4	47	53.7	110.9	38.5	63.8	47.5	54.2	110.7	68	21.4	1-1/2"	54	14.1	1-1/2"	81	25.2	2"
EAW-FD15S1PB750R3-525AXSP16	44.30	73.7	55.1	62.7	126.7	45.5	74.2	55.7	63.2	126.3	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750R3-532AXSP16	41.60	70	52	59.5	121.3	42.7	70.5	52.7	59.9	121	84	19	2"	68	16	1-1/2"	101	26.7	2"
EAW-FD15S1PB750R3-625AXSP16	46.70	77.4	57.8	66	131.5	48	77.8	58.6	66.6	131.1	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1PB750R3-632AXSP16	44.40	74.6	55.4	63.4	127.9	45.8	75.1	56.2	64	127.6	101	20.3	2"	81	13.3	2"	122	23.7	3"
EAW-FD15S1ZB370C2-425AXSP16	39.10	65.6	48.8	55.7	113.8	40.1	65.9	49.3	56.1	113.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C2-432AXSP16	36.10	61.3	45.4	52	107	37	61.5	45.9	52.3	106.5	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C2-525AXSP16	42.30	70.8	52.7	60.3	121.4	43.5	71.1	53.4	60.7	120.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C2-532AXSP16	39.80	67.4	49.8	57.1	116.4	40.9	67.6	50.4	57.5	115.7	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C2-625AXSP16	45.50	75.8	56.4	64.4	128.2	46.9	76.2	57.2	64.9	127.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C2-632AXSP16	43.60	73.5	54.3	62.3	125.6	44.9	73.9	55.1	62.7	124.9	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C4-425AXSP16	39.10	65.6	48.8	55.7	113.8	40.1	65.9	49.3	56.1	113.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C4-432AXSP16	36.10	61.3	45.4	52	107	37	61.5	45.9	52.3	106.5	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C4-525AXSP16	42.30	70.8	52.7	60.3	121.4	43.5	71.1	53.4	60.7	120.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C4-532AXSP16	39.80	67.4	49.8	57.1	116.4	40.9	67.6	50.4	57.5	115.7	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C4-625AXSP16	45.50	75.8	56.4	64.4	128.2	46.9	76.2	57.2	64.9	127.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C4-632AXSP16	43.60	73.5	54.3	62.3	125.6	44.9	73.9	55.1	62.7	124.9	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C5-425AXSP16	39.10	65.6	48.8	55.7	113.8	40.1	65.9	49.3	56.1	113.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C5-432AXSP16	36.10	61.3	45.4	52	107	37	61.5	45.9	52.3	106.5	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C5-525AXSP16	42.30	70.8	52.7	60.3	121.4	43.5	71.1	53.4	60.7	120.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C5-532AXSP16	39.80	67.4	49.8	57.1	116.4	40.9	67.6	50.4	57.5	115.7	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C5-625AXSP16	45.50	75.8	56.4	64.4	128.2	46.9	76.2	57.2	64.9	127.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C5-632AXSP16	43.60	73.5	54.3	62.3	125.6	44.9	73.9	55.1	62.7	124.9	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C8-425AXSP16	39.10	65.6	48.8	55.7	113.8	40.1	65.9	49.3	56.1	113.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C8-432AXSP16	36.10	61.3	45.4	52	107	37	61.5	45.9	52.3	106.5	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370C8-525AXSP16	42.30	70.8	52.7	60.3	121.4	43.5	71.1	53.4	60.7	120.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C8-532AXSP16	39.80	67.4	49.8	57.1	116.4	40.9	67.6	50.4	57.5	115.7	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370C8-625AXSP16	45.50	75.8	56.4	64.4	128.2	46.9	76.2	57.2	64.9	127.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370C8-632AXSP16	43.60	73.5	54.3	62.3	125.6	44.9	73.9	55.1	62.7	124.9	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370K2-425AXSP16	37.90	63.7	47.4	54.1	110.5	38.9	63.9	47.9	54.4	109.9	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370K2-432AXSP16	35.00	59.5	43.9	50.4	103.7	35.8	59.6	44.4	50.7	103.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB370K2-525AXSP16	41.30	69.1	51.5	58.9	118.4	42.4	69.4	52	59.2	117.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370K2-532AXSP16	38.60	65.5	48.4	55.5	113.1	39.7	65.7	48.9	55.8	112.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB370K2-625AXSP16	44.80	74.7	55.6	63.4	126.1	46	74.8	56.2	63.7	125.3	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB370K2-632AXSP16	42.50	71.9	53.2	60.8	122.7	43.8	72	53.8	61.2										

EAW-FD15S1ZB400C9-425AXSP16	39.10	65.6	48.8	55.7	113.8	40.1	65.9	49.3	56.1	113.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400C9-432AXSP16	36.10	61.3	45.4	52	107	37	61.5	45.9	52.3	106.5	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400C9-525AXSP16	42.30	70.8	52.7	60.3	121.4	43.5	71.1	53.4	60.7	120.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400C9-532AXSP16	39.80	67.4	49.8	57.1	116.4	40.9	67.6	50.4	57.5	115.7	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400C9-625AXSP16	45.50	75.8	56.4	64.4	128.2	46.9	76.2	57.2	64.9	127.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400C9-632AXSP16	43.60	73.5	54.3	62.3	125.6	44.9	73.9	55.1	62.7	124.9	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400K3-425AXSP16	37.90	63.7	47.4	54.1	110.5	38.9	63.9	47.9	54.4	109.9	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400K3-432AXSP16	35.00	59.5	43.9	50.4	103.7	35.8	59.6	44.4	50.7	103.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400K3-525AXSP16	41.30	69.1	51.5	58.9	118.4	42.4	69.4	52	59.2	117.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400K3-532AXSP16	38.60	65.5	48.4	55.5	113.1	39.7	65.7	48.9	55.8	112.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400K3-625AXSP16	44.80	74.7	55.6	63.4	126.1	46	74.8	56.2	63.7	125.3	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400K3-632AXSP16	42.50	71.9	53.2	60.8	122.7	43.8	72	53.8	61.2	121.8	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400K9-425AXSP16	37.90	63.7	47.4	54.1	110.5	38.9	63.9	47.9	54.4	109.9	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400K9-432AXSP16	35.00	59.5	43.9	50.4	103.7	35.8	59.6	44.4	50.7	103.2	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400K9-525AXSP16	41.30	69.1	51.5	58.9	118.4	42.4	69.4	52	59.2	117.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400K9-532AXSP16	38.60	65.5	48.4	55.5	113.1	39.7	65.7	48.9	55.8	112.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400K9-625AXSP16	44.80	74.7	55.6	63.4	126.1	46	74.8	56.2	63.7	125.3	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400K9-632AXSP16	42.50	71.9	53.2	60.8	122.7	43.8	72	53.8	61.2	121.8	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400R3-425AXSP16	38.40	64.4	48	54.8	111.7	39.3	64.7	48.5	55.1	111.1	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400R3-432AXSP16	35.40	60.2	44.5	51	104.9	36.3	60.4	45	51.4	104.4	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB400R3-525AXSP16	41.80	70	52.1	59.5	119.9	42.9	70.1	52.6	59.8	119.2	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400R3-532AXSP16	39.10	66.3	49	56.2	114.4	40.2	66.5	49.6	56.6	113.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB400R3-625AXSP16	45.30	75.4	56.1	64.1	127.5	46.5	75.7	56.8	64.4	126.8	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB400R3-632AXSP16	43.10	72.6	53.8	61.5	124	44.3	72.8	54.4	61.9	123.2	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550B3-425AXSP16	40.70	68.2	50.7	57.9	118.4	41.8	68.6	51.3	58.3	118.1	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550B3-432AXSP16	37.70	63.9	47.3	54.1	111.7	38.7	64.2	47.9	54.5	111.3	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550B3-525AXSP16	43.70	73.1	54.5	62.3	125.6	45	73.6	55.2	62.7	125.2	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550B3-532AXSP16	41.30	69.8	51.7	59.3	120.8	42.5	70.2	52.3	59.8	120.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550B3-625AXSP16	-	-	-	-	-	-	-	-	-	-	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C3-632AXSP16	-	-	-	-	-	46.4	76.3	57	64.9	129.4	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C2-425AXSP16	43.50	72.7	54	61.7	-	44.5	73	54.6	62.1	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C2-432AXSP16	40.00	67.6	50.1	57.3	118.3	41	68	50.7	57.7	117.8	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C2-525AXSP16	47.20	78.8	58.8	67	135.6	48.5	79.3	59.6	67.5	135.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C2-532AXSP16	44.20	74.5	55.3	63.2	129.2	45.4	74.9	55.9	63.8	128.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C2-625AXSP16	51.10	84.7	63.4	72.3	144.1	52.5	85.3	64.2	72.9	143.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C2-632AXSP16	48.60	81.7	60.6	69.4	140.1	50	82.1	61.4	70	139.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C3-425AXSP16	43.50	72.7	54	61.7	-	44.5	73	54.6	62.1	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C3-432AXSP16	40.00	67.6	50.1	57.3	118.3	41	68	50.7	57.7	117.8	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C3-525AXSP16	47.20	78.8	58.8	67	135.6	48.5	79.3	59.6	67.5	135.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C3-532AXSP16	44.20	74.5	55.3	63.2	129.2	45.4	74.9	55.9	63.8	128.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C3-625AXSP16	51.10	84.7	63.4	72.3	144.1	52.5	85.3	64.2	72.9	143.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C3-632AXSP16	48.60	81.7	60.6	69.4	140.1	50	82.1	61.4	70	139.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C4-425AXSP16	43.50	72.7	54	61.7	-	44.5	73	54.6	62.1	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C4-432AXSP16	40.00	67.6	50.1	57.3	118.3	41	68	50.7	57.7	117.8	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C4-525AXSP16	47.20	78.8	58.8	67	135.6	48.5	79.3	59.6	67.5	135.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C4-532AXSP16	44.20	74.5	55.3	63.2	129.2	45.4	74.9	55.9	63.8	128.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C4-625AXSP16	51.10	84.7	63.4	72.3	144.1	52.5	85.3	64.2	72.9	143.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C4-632AXSP16	48.60	81.7	60.6	69.4	140.1	50	82.1	61.4	70	139.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C5-425AXSP16	43.50	72.7	54	61.7	-	44.5	73	54.6	62.1	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C5-432AXSP16	40.00	67.6	50.1	57.3	118.3	41	68	50.7	57.7	117.8	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C5-525AXSP16	47.20	78.8	58.8	67	135.6	48.5	79.3	59.6	67.5	135.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C5-532AXSP16	44.20	74.5	55.3	63.2	129.2	45.4	74.9	55.9	63.8	128.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C5-625AXSP16	51.10	84.7	63.4	72.3	144.1	52.5	85.3	64.2	72.9	143.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C5-632AXSP16	48.60	81.7	60.6	69.4	140.1	50	82.1	61.4	70	139.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C8-425AXSP16	43.50	72.7	54	61.7	-	44.5	73	54.6	62.1	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C8-432AXSP16	40.00	67.6	50.1	57.3	118.3	41	68	50.7	57.7	117.8	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C8-525AXSP16	47.20	78.8	58.8	67	135.6	48.5	79.3	59.6	67.5	135.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C8-532AXSP16	44.20	74.5	55.3	63.2	129.2	45.4	74.9	55.9	63.8	128.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C8-625AXSP16	51.10	84.7	63.4	72.3	144.1	52.5	85.3	64.2	72.9	143.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C8-632AXSP16	48.60	81.7	60.6	69.4	140.1	50	82.1	61.4	70	139.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550C9-425AXSP16	43.50	72.7	54	61.7	-	44.5	73	54.6	62.1	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C9-432AXSP16	40.00	67.6	50.1	57.3	118.3	41	68	50.7	57.7	117.8	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550C9-525AXSP16	47.20	78.8	58.8	67	135.6	48.5	79.3	59.6	67.5	135.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C9-532AXSP16	44.20	74.5	55.3	63.2	129.2	45.4	74.9	55.9	63.8	128.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550C9-625AXSP16	51.10	84.7	63.4	72.3	144.1	52.5	85.3	64.2	72.9	143.6	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1Z																			

EAW-FD15S1ZB550K9-632AXSP16	46.60	78.6	58.3	66.7	134.5	48	78.9	58.9	67.1	133.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550R3-425AXSP16	42.40	70.9	52.8	60.2	-	43.4	71.3	53.3	60.7	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550R3-432AXSP16	39.00	66.1	49	56	115.6	40	66.4	49.5	56.4	115.1	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB550R3-525AXSP16	46.20	77.1	57.5	65.6	132.6	47.4	77.5	58.2	66	132.1	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550R3-532AXSP16	43.10	72.8	54	61.8	126.2	44.3	73.1	54.6	62.3	125.7	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB550R3-625AXSP16	50.10	83.2	62.1	70.9	141.3	51.5	83.6	62.9	71.3	140.7	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB550R3-632AXSP16	47.60	80	59.4	67.9	137.2	48.9	80.4	60.1	68.4	136.4	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K2-425AXSP16	44.00	73.6	54.6	62.4	-	45.1	73.9	55.3	62.8	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K2-432AXSP16	40.50	68.4	50.7	58	119.9	41.5	68.9	51.3	58.4	119.6	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K2-525AXSP16	47.90	79.7	59.6	67.8	137.3	49.1	80.1	60.3	68.3	136.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K2-532AXSP16	44.70	75.4	55.9	64	130.7	45.9	75.8	56.6	64.5	130.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K2-625AXSP16	51.80	85.9	64.2	73.2	146	53.3	86.4	65	73.8	145.5	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K2-632AXSP16	49.20	82.7	61.4	70.3	141.8	50.6	83.1	62.2	70.8	141.2	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K3-425AXSP16	44.00	73.6	54.6	62.4	-	45.1	73.9	55.3	62.8	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K3-432AXSP16	40.50	68.4	50.7	58	119.9	41.5	68.9	51.3	58.4	119.6	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K3-525AXSP16	47.90	79.7	59.6	67.8	137.3	49.1	80.1	60.3	68.3	136.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K3-532AXSP16	44.70	75.4	55.9	64	130.7	45.9	75.8	56.6	64.5	130.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K3-625AXSP16	51.80	85.9	64.2	73.2	146	53.3	86.4	65	73.8	145.5	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K3-632AXSP16	49.20	82.7	61.4	70.3	141.8	50.6	83.1	62.2	70.8	141.2	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K4-425AXSP16	44.00	73.6	54.6	62.4	-	45.1	73.9	55.3	62.8	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K4-432AXSP16	40.50	68.4	50.7	58	119.9	41.5	68.9	51.3	58.4	119.6	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K4-525AXSP16	47.90	79.7	59.6	67.8	137.3	49.1	80.1	60.3	68.3	136.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K4-532AXSP16	44.70	75.4	55.9	64	130.7	45.9	75.8	56.6	64.5	130.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K4-625AXSP16	51.80	85.9	64.2	73.2	146	53.3	86.4	65	73.8	145.5	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K4-632AXSP16	49.20	82.7	61.4	70.3	141.8	50.6	83.1	62.2	70.8	141.2	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K9-425AXSP16	44.00	73.6	54.6	62.4	-	45.1	73.9	55.3	62.8	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K9-432AXSP16	40.50	68.4	50.7	58	119.9	41.5	68.9	51.3	58.4	119.6	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750K9-525AXSP16	47.90	79.7	59.6	67.8	137.3	49.1	80.1	60.3	68.3	136.8	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K9-532AXSP16	44.70	75.4	55.9	64	130.7	45.9	75.8	56.6	64.5	130.4	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750K9-625AXSP16	51.80	85.9	64.2	73.2	146	53.3	86.4	65	73.8	145.5	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750K9-632AXSP16	49.20	82.7	61.4	70.3	141.8	50.6	83.1	62.2	70.8	141.2	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750R3-425AXSP16	43.10	72	53.5	61.1	-	44.1	72.5	54.2	61.6	-	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750R3-432AXSP16	39.70	67.1	49.7	56.9	117.4	40.7	67.5	50.3	57.3	117	73	18.4	2"	59	14.8	1-1/2"	88	25.8	2"
EAW-FD15S1ZB750R3-525AXSP16	46.80	78	58.2	66.4	134.4	48	78.5	59	66.9	133.9	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750R3-532AXSP16	43.70	73.8	54.8	62.8	128.1	44.9	74.2	55.4	63.2	127.5	90	19.5	2"	72	12.8	2"	108	27.4	2"
EAW-FD15S1ZB750R3-625AXSP16	50.70	84.1	62.8	71.7	142.8	52.1	84.5	63.6	72.2	142.3	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZB750R3-632AXSP16	48.20	81	60	68.7	138.9	49.6	81.5	60.8	69.3	138.3	113	21.3	2"	90	14.1	2"	135	24	3"
EAW-FD15S1ZK370C2-425AXSP16	43.20	71.1	53.3	60.6	-	44	71.2	53.6	60.8	121.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C2-432AXSP16	39.90	66.4	49.5	56.4	115	40.6	66.5	49.8	56.6	114.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C2-525AXSP16	47.10	77	58	65.8	131.2	48	77.2	58.3	65.9	130.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C2-532AXSP16	44.10	73.2	54.6	62.3	125.6	45	73.2	55	62.5	124.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C2-625AXSP16	50.80	82.8	62.4	70.8	139.1	51.9	83	62.9	71	138.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C2-632AXSP16	48.60	80.1	59.9	68.2	135.8	49.6	80.2	60.3	68.5	134.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C4-425AXSP16	43.20	71.1	53.3	60.6	-	44	71.2	53.6	60.8	121.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C4-432AXSP16	39.90	66.4	49.5	56.4	115	40.6	66.5	49.8	56.6	114.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C4-525AXSP16	47.10	77	58	65.8	131.2	48	77.2	58.3	65.9	130.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C4-532AXSP16	44.10	73.2	54.6	62.3	125.6	45	73.2	55	62.5	124.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C4-625AXSP16	50.80	82.8	62.4	70.8	139.1	51.9	83	62.9	71	138.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C4-632AXSP16	48.60	80.1	59.9	68.2	135.8	49.6	80.2	60.3	68.5	134.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C5-425AXSP16	43.20	71.1	53.3	60.6	-	44	71.2	53.6	60.8	121.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C5-432AXSP16	39.90	66.4	49.5	56.4	115	40.6	66.5	49.8	56.6	114.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C5-525AXSP16	47.10	77	58	65.8	131.2	48	77.2	58.3	65.9	130.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C5-532AXSP16	44.10	73.2	54.6	62.3	125.6	45	73.2	55	62.5	124.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C5-625AXSP16	50.80	82.8	62.4	70.8	139.1	51.9	83	62.9	71	138.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C5-632AXSP16	48.60	80.1	59.9	68.2	135.8	49.6	80.2	60.3	68.5	134.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C8-425AXSP16	43.20	71.1	53.3	60.6	-	44	71.2	53.6	60.8	121.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C8-432AXSP16	39.90	66.4	49.5	56.4	115	40.6	66.5	49.8	56.6	114.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370C8-525AXSP16	47.10	77	58	65.8	131.2	48	77.2	58.3	65.9	130.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C8-532AXSP16	44.10	73.2	54.6	62.3	125.6	45	73.2	55	62.5	124.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370C8-625AXSP16	50.80	82.8	62.4	70.8	139.1	51.9	83	62.9	71	138.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370C8-632AXSP16	48.60	80.1	59.9	68.2	135.8	49.6	80.2	60.3	68.5	134.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK370K2-425AXSP16	41.80	68.9	51.5	58.6	118.5	42.5	68.9	51.9	58.7	117.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370K2-432AXSP16	38.50	64.2	47.9	54.6	111	39.2	64.3	48.1	54.7	110.3	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK370K2-525AXSP16	45.70	74.8	56.2	63.9	127.3	46.5	74.8	56.6	64	126.3	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK370K2-532AXSP16	42.70	70.9	52.9	60.4	121.5	43.5	70.9	53.2	60.5	120.5	90	20.8	2"	72	13.7	2"			

EAW-FD1551ZK400B3-625AXSP16	48.70	79.3	59.7	67.7	133.1	49.7	79.5	60.2	68	132.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400B3-632AXSP16	46.60	77.1	57.6	65.6	130.4	47.7	77.2	58.1	65.9	129.7	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400C3-425AXSP16	43.20	71.1	53.3	60.6	-	44	71.2	53.6	60.8	121.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400C3-432AXSP16	39.90	66.4	49.5	56.4	115	40.6	66.5	49.8	56.6	114.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400C3-525AXSP16	47.10	77	58	65.8	131.2	48	77.2	58.3	65.9	130.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400C3-532AXSP16	44.10	73.2	54.6	62.3	125.6	45	73.2	55	62.5	124.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400C3-625AXSP16	50.80	82.8	62.4	70.8	139.1	51.9	83	62.9	71	138.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400C3-632AXSP16	48.60	80.1	59.9	68.2	135.8	49.6	80.2	60.3	68.5	134.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400C9-425AXSP16	43.20	71.1	53.3	60.6	-	44	71.2	53.6	60.8	121.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400C9-432AXSP16	39.90	66.4	49.5	56.4	115	40.6	66.5	49.8	56.6	114.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400C9-525AXSP16	47.10	77	58	65.8	131.2	48	77.2	58.3	65.9	130.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400C9-532AXSP16	44.10	73.2	54.6	62.3	125.6	45	73.2	55	62.5	124.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400C9-625AXSP16	50.80	82.8	62.4	70.8	139.1	51.9	83	62.9	71	138.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400C9-632AXSP16	48.60	80.1	59.9	68.2	135.8	49.6	80.2	60.3	68.5	134.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400K3-425AXSP16	41.80	68.9	51.5	58.6	118.5	42.5	68.9	51.9	58.7	117.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400K3-432AXSP16	38.50	64.2	47.9	54.6	111	39.2	64.3	48.1	54.7	110.3	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400K3-525AXSP16	45.70	74.8	56.2	63.9	127.3	46.5	74.8	56.6	64	126.3	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400K3-532AXSP16	42.70	70.9	52.9	60.4	121.5	43.5	70.9	53.2	60.5	120.5	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400K3-625AXSP16	49.60	80.8	60.8	69	135.7	50.5	80.8	61.2	69.1	134.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400K3-632AXSP16	47.20	77.8	58.2	66.2	131.7	48.1	77.8	58.6	66.3	130.7	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400K9-425AXSP16	41.80	68.9	51.5	58.6	118.5	42.5	68.9	51.9	58.7	117.6	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400K9-432AXSP16	38.50	64.2	47.9	54.6	111	39.2	64.3	48.1	54.7	110.3	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400K9-525AXSP16	45.70	74.8	56.2	63.9	127.3	46.5	74.8	56.6	64	126.3	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400K9-532AXSP16	42.70	70.9	52.9	60.4	121.5	43.5	70.9	53.2	60.5	120.5	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400K9-625AXSP16	49.60	80.8	60.8	69	135.7	50.5	80.8	61.2	69.1	134.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400K9-632AXSP16	47.20	77.8	58.2	66.2	131.7	48.1	77.8	58.6	66.3	130.7	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400R3-425AXSP16	42.40	69.7	52.2	59.4	120	43.1	69.9	52.5	59.6	119.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400R3-432AXSP16	39.10	65.1	48.5	55.3	112.8	39.8	65.1	48.9	55.4	111.9	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK400R3-525AXSP16	46.20	75.8	56.9	64.7	128.9	47.1	75.8	57.3	64.8	128	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400R3-532AXSP16	43.30	71.8	53.5	61.2	123.1	44.1	71.8	53.9	61.3	122.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK400R3-625AXSP16	50.20	81.7	61.5	69.8	137.3	51.2	81.8	61.9	70	136.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK400R3-632AXSP16	47.70	78.8	58.8	67.1	133.4	48.7	78.7	59.3	67.2	132.4	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550B3-425AXSP16	45.30	74.5	55.6	63.3	-	46.1	74.6	56.1	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550B3-432AXSP16	41.90	69.5	51.8	59.1	120.7	42.6	69.8	52.2	59.4	120.1	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550B3-525AXSP16	49.00	80.2	60.3	68.4	136.8	50	80.5	60.8	68.7	136.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550B3-532AXSP16	46.10	76.3	57.1	64.9	131.2	47	76.5	57.5	65.3	130.5	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550B3-625AXSP16	52.70	85.8	64.6	73.4	144.2	53.9	86.1	65.2	73.8	143.6	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550B3-632AXSP16	50.50	83.3	62.4	71	141.3	51.7	83.6	63	71.3	140.6	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C2-425AXSP16	48.10	79.1	59	67.2	-	49	79.2	59.4	67.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C2-432AXSP16	44.20	73.4	54.6	62.3	-	45	73.5	55	62.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C2-525AXSP16	52.70	85.9	64.5	73.3	147	53.6	86.2	65.1	73.6	146.2	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C2-532AXSP16	49.10	81.1	60.7	69.1	139.9	50.1	81.3	61.2	69.4	138.9	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C2-625AXSP16	57.20	92.8	70.1	79.4	156.7	58.3	93.1	70.6	79.7	155.8	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C2-632AXSP16	54.30	89.3	67	76.3	152	55.5	89.5	67.4	76.5	151.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C3-425AXSP16	48.10	79.1	59	67.2	-	49	79.2	59.4	67.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C3-432AXSP16	44.20	73.4	54.6	62.3	-	45	73.5	55	62.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C3-525AXSP16	52.70	85.9	64.5	73.3	147	53.6	86.2	65.1	73.6	146.2	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C3-532AXSP16	49.10	81.1	60.7	69.1	139.9	50.1	81.3	61.2	69.4	138.9	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C3-625AXSP16	57.20	92.8	70.1	79.4	156.7	58.3	93.1	70.6	79.7	155.8	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C3-632AXSP16	54.30	89.3	67	76.3	152	55.5	89.5	67.4	76.5	151.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C4-425AXSP16	48.10	79.1	59	67.2	-	49	79.2	59.4	67.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C4-525AXSP16	44.20	73.4	54.6	62.3	-	45	73.5	55	62.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C4-532AXSP16	52.70	85.9	64.5	73.3	147	53.6	86.2	65.1	73.6	146.2	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C4-625AXSP16	49.10	81.1	60.7	69.1	139.9	50.1	81.3	61.2	69.4	138.9	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C4-632AXSP16	57.20	92.8	70.1	79.4	156.7	58.3	93.1	70.6	79.7	155.8	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C5-425AXSP16	48.10	79.1	59	67.2	-	49	79.2	59.4	67.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C5-432AXSP16	44.20	73.4	54.6	62.3	-	45	73.5	55	62.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C5-432AXSP16	44.20	73.4	54.6	62.3	-	45	73.5	55	62.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C5-525AXSP16	52.70	85.9	64.5	73.3	147	53.6	86.2	65.1	73.6	146.2	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C5-532AXSP16	49.10	81.1	60.7	69.1	139.9	50.1	81.3	61.2	69.4	138.9	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD1551ZK550C5-625AXSP16	57.20	92.8	70.1	79.4	156.7	58.3	93.1	70.6	79.7	155.8	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C5-632AXSP16	54.30	89.3	67	76.3	152	55.5	89.5	67.4	76.5	151.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD1551ZK550C8-425AXSP16	48.10	79.1	59	67.2	-	49	79.2	59.4	67.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C8-432AXSP16	44.20	73.4	54.6	62.3	-	45	73.5	55	62.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD1551ZK550C8-525AXSP16	52.70	85.9	64.5	73.3	147	53.6	86.2	65.1	73.6	146.2	90	20.8	2"	72	13.7	2"	108	29.2	

EAW-FD15S1ZK550K8-532AXSP16	46.90	77.6	58.1	66.1	133.5	47.8	77.8	58.4	66.3	132.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK550K8-625AXSP16	54.70	89	67.1	76.1	149.8	55.7	89	67.4	76.2	148.6	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK550K8-632AXSP16	51.90	85.4	63.9	72.8	145.2	52.9	85.5	64.4	73	144	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK550K9-425AXSP16	46.00	75.6	56.4	64.3	-	46.8	75.7	56.9	64.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK550K9-432AXSP16	42.30	70.3	52.3	59.7	122	43	70.4	52.7	59.9	121.2	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK550K9-525AXSP16	50.20	82.1	61.7	70.1	140.3	51.1	82.3	62.2	70.3	139.3	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK550K9-532AXSP16	46.90	77.6	58.1	66.1	133.5	47.8	77.8	58.4	66.3	132.7	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK550K9-625AXSP16	54.70	89	67.1	76.1	149.8	55.7	89	67.4	76.2	148.6	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK550K9-632AXSP16	51.90	85.4	63.9	72.8	145.2	52.9	85.5	64.4	73	144	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK550R3-425AXSP16	47.00	77.1	57.6	65.6	-	47.8	77.3	58	65.8	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK550R3-432AXSP16	43.20	71.7	53.4	60.9	-	44	71.9	53.8	61.1	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK550R3-525AXSP16	51.30	83.8	63	71.5	143.1	52.2	83.9	63.4	71.8	142.3	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK550R3-532AXSP16	47.90	79.2	59.3	67.4	136.3	48.8	79.4	59.7	67.7	135.4	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK550R3-625AXSP16	55.80	90.8	68.5	77.6	152.9	56.9	90.8	68.9	77.9	151.8	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK550R3-632AXSP16	52.90	87.2	65.2	74.4	148.2	54	87.3	65.8	74.6	147.1	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750C4-425AXSP16	50.20	82.5	61.6	70.1	-	51.1	82.9	62.1	70.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750C4-432AXSP16	46.30	76.8	57.1	65.2	-	47.2	77	57.6	65.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750C4-532AXSP16	54.70	89.4	67	76.2	-	55.8	89.8	67.8	76.6	-	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750C4-532AXSP16	51.20	84.5	63.2	71.9	145.8	52.3	84.9	63.8	72.4	145.2	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750C5-625AXSP16	56.40	92.8	69.5	79.1	158.1	57.7	93.2	70.2	79.5	157.4	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750C5-425AXSP16	50.20	82.5	61.6	70.1	-	51.1	82.9	62.1	70.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750C5-432AXSP16	46.30	76.8	57.1	65.2	-	47.2	77	57.6	65.5	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750C5-525AXSP16	54.70	89.4	67	76.2	-	55.8	89.8	67.8	76.6	-	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750C5-532AXSP16	51.20	84.5	63.2	71.9	145.8	52.3	84.9	63.8	72.4	145.2	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750C5-632AXSP16	56.40	92.8	69.5	79.1	158.1	57.7	93.2	70.2	79.5	157.4	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K2-425AXSP16	48.80	80.1	59.8	68.1	-	49.6	80.3	60.3	68.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K2-432AXSP16	45.00	74.6	55.5	63.3	-	45.8	74.7	55.9	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K2-525AXSP16	53.30	87	65.3	74.2	148.8	54.2	87.2	65.9	74.5	148.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K2-532AXSP16	49.70	82.2	61.5	70	141.6	50.7	82.5	61.9	70.2	140.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K2-625AXSP16	57.90	94	70.9	80.4	158.8	59.1	94.3	71.5	80.8	158	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K2-632AXSP16	55.00	90.3	67.7	77.2	153.9	56.1	90.6	68.4	77.4	152.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K3-425AXSP16	48.80	80.1	59.8	68.1	-	49.6	80.3	60.3	68.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K3-432AXSP16	45.00	74.6	55.5	63.3	-	45.8	74.7	55.9	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K3-525AXSP16	53.30	87	65.3	74.2	148.8	54.2	87.2	65.9	74.5	148.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K3-532AXSP16	49.70	82.2	61.5	70	141.6	50.7	82.5	61.9	70.2	140.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K3-625AXSP16	57.90	94	70.9	80.4	158.8	59.1	94.3	71.5	80.8	158	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K3-632AXSP16	55.00	90.3	67.7	77.2	153.9	56.1	90.6	68.4	77.4	152.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K4-425AXSP16	48.80	80.1	59.8	68.1	-	49.6	80.3	60.3	68.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K4-432AXSP16	45.00	74.6	55.5	63.3	-	45.8	74.7	55.9	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K4-525AXSP16	53.30	87	65.3	74.2	148.8	54.2	87.2	65.9	74.5	148.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K4-532AXSP16	49.70	82.2	61.5	70	141.6	50.7	82.5	61.9	70.2	140.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K4-625AXSP16	57.90	94	70.9	80.4	158.8	59.1	94.3	71.5	80.8	158	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K4-632AXSP16	55.00	90.3	67.7	77.2	153.9	56.1	90.6	68.4	77.4	152.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K5-425AXSP16	48.80	80.1	59.8	68.1	-	49.6	80.3	60.3	68.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K5-432AXSP16	45.00	74.6	55.5	63.3	-	45.8	74.7	55.9	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K5-525AXSP16	53.30	87	65.3	74.2	148.8	54.2	87.2	65.9	74.5	148.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K5-532AXSP16	49.70	82.2	61.5	70	141.6	50.7	82.5	61.9	70.2	140.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K5-625AXSP16	57.90	94	70.9	80.4	158.8	59.1	94.3	71.5	80.8	158	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K5-632AXSP16	55.00	90.3	67.7	77.2	153.9	56.1	90.6	68.4	77.4	152.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K8-425AXSP16	48.80	80.1	59.8	68.1	-	49.6	80.3	60.3	68.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K8-432AXSP16	45.00	74.6	55.5	63.3	-	45.8	74.7	55.9	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K8-532AXSP16	53.30	87	65.3	74.2	148.8	54.2	87.2	65.9	74.5	148.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K8-632AXSP16	49.70	82.2	61.5	70	141.6	50.7	82.5	61.9	70.2	140.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K8-625AXSP16	57.90	94	70.9	80.4	158.8	59.1	94.3	71.5	80.8	158	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K8-632AXSP16	55.00	90.3	67.7	77.2	153.9	56.1	90.6	68.4	77.4	152.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K9-425AXSP16	48.80	80.1	59.8	68.1	-	49.6	80.3	60.3	68.4	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K9-432AXSP16	45.00	74.6	55.5	63.3	-	45.8	74.7	55.9	63.6	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750K9-525AXSP16	53.30	87	65.3	74.2	148.8	54.2	87.2	65.9	74.5	148.1	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K9-532AXSP16	49.70	82.2	61.5	70	141.6	50.7	82.5	61.9	70.2	140.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750K9-625AXSP16	57.90	94	70.9	80.4	158.8	59.1	94.3	71.5	80.8	158	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750K9-632AXSP16	55.00	90.3	67.7	77.2	153.9	56.1	90.6	68.4	77.4	152.9	113	22.7	2"	90	14.9	2"	135	25.9	3"
EAW-FD15S1ZK750R3-425AXSP16	47.80	78.5	58.6	66.7	-	48.6	78.7	59	67	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750R3-432AXSP16	44.00	73.1	54.4	62	-	44.9	73.3	54.8	62.3	-	73	19.7	2"	59	15.7	1-1/2"	88	27.6	2"
EAW-FD15S1ZK750R3-525AXSP16	52.20	85.2	63.9	72.6	145.5	53.1	85.4	64.5	72.8	144.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750R3-532AXSP16	48.70	80.6	60.2	68.5	138.6	49.7	80.7	60.7	68.9	137.8	90	20.8	2"	72	13.7	2"	108	29.2	2"
EAW-FD15S1ZK750R3-625AXSP16	56.60	92	69.4																

EAW-FD1552PB370K4-625AXSP12	92.30	144	110	123.6	-	93	143.5	110.1	123.5	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB370K4-632AXSP12	88.20	139.1	105.9	119.3	-	88.9	138.7	106	119.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB370K5-425AXSP12	78.70	125.9	95	107.7	-	79.4	125.7	95.3	107.5	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB370K5-432AXSP12	73.10	117.7	88.6	100.4	-	73.7	117.5	88.8	100.4	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB370K5-525AXSP12	86.80	137.1	104.2	117.4	-	87.5	136.8	104.3	117.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB370K5-532AXSP12	81.90	130.3	98.6	111.4	-	82.5	130	98.8	111.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB370K5-625AXSP12	92.30	144	110	123.6	-	93	143.5	110.1	123.5	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB370K5-632AXSP12	88.20	139.1	105.9	119.3	-	88.9	138.7	106	119.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB370K8-425AXSP12	78.70	125.9	95	107.7	-	79.4	125.7	95.3	107.5	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB370K8-432AXSP12	73.10	117.7	88.6	100.4	-	73.7	117.5	88.8	100.4	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB370K8-525AXSP12	86.80	137.1	104.2	117.4	-	87.5	136.8	104.3	117.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB370K8-532AXSP12	81.90	130.3	98.6	111.4	-	82.5	130	98.8	111.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB370K8-625AXSP12	92.30	144	110	123.6	-	93	143.5	110.1	123.5	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB370K8-632AXSP12	88.20	139.1	105.9	119.3	-	88.9	138.7	106	119.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400B3-425AXSP12	77.60	123.9	93.6	106	-	78.4	124	94	106.2	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400B3-432AXSP12	72.60	116.8	87.9	99.6	-	73.3	116.8	88.3	99.8	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400B3-525AXSP08	-	-	-	-	-	-	-	-	-	-	169	16.2	3"	135	10.7	3"	203	22.7	3"
EAW-FD1552PB400B3-532AXSP12	80.40	127.8	96.8	109.4	-	81.1	128	97.1	109.4	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.1	3"	162	11.3	3"	244	24.1	3"
EAW-FD1552PB400B3-632AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.1	3"	162	11.3	3"	244	24.1	3"
EAW-FD1552PB400C3-425AXSP08	73.40	123.1	91.6	104.5	213.5	75.3	123.8	92.7	105.3	212.8	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB400C3-432AXSP12	75.10	120.9	91	103.1	-	75.8	120.9	91.2	103.1	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400C3-525AXSP12	88.00	138.8	105.6	119	-	88.8	139	105.9	119.1	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400C3-532AXSP12	83.50	133	100.5	113.6	-	84.3	133	101	113.9	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400C3-625AXSP12	92.60	144.3	110.3	124	-	93.4	144.4	110.8	124.3	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400C3-632AXSP12	89.20	140.7	107.1	120.7	-	90.2	140.8	107.5	120.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400C3-425AXSP08	73.40	123.1	91.6	104.5	213.5	75.3	123.8	92.7	105.3	212.8	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB400C3-432AXSP12	75.10	120.9	91	103.1	-	75.8	120.9	91.2	103.1	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400C3-525AXSP12	88.00	138.8	105.6	119	-	88.8	139	105.9	119.1	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400C3-532AXSP12	83.50	133	100.5	113.6	-	84.3	133	101	113.9	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400C3-625AXSP12	92.60	144.3	110.3	124	-	93.4	144.4	110.8	124.3	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400C3-632AXSP12	89.20	140.7	107.1	120.7	-	90.2	140.8	107.5	120.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400K3-425AXSP12	78.70	125.9	95	107.7	-	79.4	125.7	95.3	107.5	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400K3-432AXSP12	73.10	117.7	88.6	100.4	-	73.7	117.5	88.8	100.4	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400K3-525AXSP12	86.80	137.1	104.2	117.4	-	87.5	136.8	104.3	117.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400K3-532AXSP12	81.90	130.3	98.6	111.4	-	82.5	130	98.8	111.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400K3-625AXSP12	92.30	144	110	123.6	-	93	143.5	110.1	123.5	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400K3-632AXSP12	88.20	139.1	105.9	119.3	-	88.9	138.7	106	119.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400K3-425AXSP12	78.70	125.9	95	107.7	-	79.4	125.7	95.3	107.5	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400K3-432AXSP12	73.10	117.7	88.6	100.4	-	73.7	117.5	88.8	100.4	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400K3-525AXSP12	86.80	137.1	104.2	117.4	-	87.5	136.8	104.3	117.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400K3-532AXSP12	81.90	130.3	98.6	111.4	-	82.5	130	98.8	111.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400K3-625AXSP12	92.30	144	110	123.6	-	93	143.5	110.1	123.5	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400K3-632AXSP12	88.20	139.1	105.9	119.3	-	88.9	138.7	106	119.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400R3-425AXSP12	79.60	127.2	96.2	108.8	-	80.2	127.1	96.3	108.6	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400R3-432AXSP12	73.90	119	89.6	101.6	-	74.5	118.9	89.8	101.6	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB400R3-525AXSP12	87.50	138.3	105.2	118.6	-	88.4	138.1	105.4	118.5	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400R3-532AXSP12	82.70	131.8	99.7	112.7	-	83.3	131.6	99.7	112.4	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB400R3-625AXSP12	93.10	145.3	111	124.7	-	93.7	144.9	111.2	124.7	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB400R3-632AXSP12	89.10	140.4	106.7	120.2	-	89.8	140.1	107	120.3	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550B3-425AXSP08	75.80	127.1	94.5	107.8	220.6	77.9	128	95.7	108.9	220.4	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550B3-432AXSP12	77.60	125.2	94.2	106.7	-	78.4	125.3	94.5	106.9	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB550B3-525AXSP08	-	-	-	-	-	-	-	-	-	-	169	16.2	3"	135	10.7	3"	203	22.7	3"
EAW-FD1552PB550B3-532AXSP12	-	-	-	-	-	86.9	137.1	104.1	117.4	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.1	3"	162	11.3	3"	244	24.1	3"
EAW-FD1552PB550B3-632AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.1	3"	162	11.3	3"	244	24.1	3"
EAW-FD1552PB550C2-425AXSP08	81.50	136.2	101.2	115.6	-	83.6	137	102.5	116.6	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550C2-432AXSP08	75.20	127.1	94.1	107.7	222.6	77.1	128	95.3	108.5	222.2	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550C2-525AXSP12	97.40	154.5	117.1	132.3	-	98.4	154.8	117.6	132.5	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550C2-532AXSP12	92.00	147.2	111.1	125.6	-	93	147.2	111.6	125.8	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550C2-632AXSP12	-	-	-	-	-	99.8	156.3	119.1	134	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550C3-425AXSP08	81.50	136.2	101.2	115.6	-	83.6	137	102.5	116.6	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550C3-432AXSP08	75.20	127.1	94.1	107.7	222.6	77.1	128	95.3	108.5	222.2	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550C3-525AXSP12	97.40	154.5	117.1	132.3	-	98.4	154.8	117.6	132.5	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550C3-532AXSP12	92.00	147.2	111.1	125.6	-	93	147.2	111.6	125.8	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550C3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.1	3"	162	11.3	3"	244	24.1	3"
EAW-FD1552PB550C3-632AXSP12	-	-	-	-	-	99.8	156.3	119.1	134	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550C4-425AXSP08	81.50	136.2	101.2	115.6	-	83.6	137	102.5	116.6	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550C4-432AXSP08																			

EAW-FD1552PB550K4-432AXSP12	79.30	128	96.2	109.1	-	80	127.9	96.5	109.2	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB550K4-525AXSP12	94.30	149.2	113.3	127.9	-	95	149.1	113.7	127.8	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K4-532AXSP12	88.80	141.9	107.1	121.2	-	89.5	141.6	107.3	121.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K4-625AXSP12	100.30	156.9	119.6	134.6	-	101.1	156.7	120.1	134.6	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K4-632AXSP12	95.70	151.1	114.9	129.5	-	96.6	151	115.2	129.6	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K5-425AXSP08	78.30	130.9	97.4	111.2	-	80.2	131.6	98.5	112.1	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550K5-432AXSP12	79.30	128	96.2	109.1	-	80	127.9	96.5	109.2	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB550K5-525AXSP12	94.30	149.2	113.3	127.9	-	95	149.1	113.7	127.8	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K5-532AXSP12	88.80	141.9	107.1	121.2	-	89.5	141.6	107.3	121.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K5-625AXSP12	100.30	156.9	119.6	134.6	-	101.1	156.7	120.1	134.6	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K5-632AXSP12	95.70	151.1	114.9	129.5	-	96.6	151	115.2	129.6	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K8-425AXSP08	78.30	130.9	97.4	111.2	-	80.2	131.6	98.5	112.1	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550K8-432AXSP12	79.30	128	96.2	109.1	-	80	127.9	96.5	109.2	-	90	24.2	2"	72	16	2"	108	34	2"
EAW-FD1552PB550K8-525AXSP12	94.30	149.2	113.3	127.9	-	95	149.1	113.7	127.8	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K8-532AXSP12	88.80	141.9	107.1	121.2	-	89.5	141.6	107.3	121.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K8-625AXSP12	100.30	156.9	119.6	134.6	-	101.1	156.7	120.1	134.6	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K8-632AXSP12	95.70	151.1	114.9	129.5	-	96.6	151	115.2	129.6	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K9-425AXSP08	79.80	133.5	99.1	113.2	-	81.7	134.3	100.3	114	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550K9-432AXSP08	73.40	124.3	92.1	105.3	217.5	75.4	125.1	93.2	106.2	216.8	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB550K9-525AXSP12	95.80	151.9	115.1	130	-	96.7	152	115.6	130.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K9-532AXSP12	90.30	144.2	109	123.2	-	91.1	144.1	109.4	123.3	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB550K9-625AXSP12	100.00	159.7	121.7	137	-	102.7	159.5	122.2	137	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB550K9-632AXSP12	97.30	153.8	116.9	131.8	-	98.2	153.8	117.2	131.7	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K2-425AXSP08	82.40	137.7	102.3	116.8	-	84.5	138.6	103.6	117.9	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K2-432AXSP08	76.00	128.5	95.1	108.9	225.1	78	129.3	96.3	109.7	224.7	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K2-525AXSP12	98.70	156.6	118.7	133.8	-	99.6	156.6	119.1	134.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K2-532AXSP12	93.00	148.8	112.3	127	-	93.9	148.9	112.8	127.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K2-625AXSP12	104.80	164.3	125.1	140.9	-	105.7	164.4	125.8	141.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K3-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K3-425AXSP08	82.40	137.7	102.3	116.8	-	84.5	138.6	103.6	117.9	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K3-432AXSP08	76.00	128.5	95.1	108.9	225.1	78	129.3	96.3	109.7	224.7	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K3-525AXSP12	98.70	156.6	118.7	133.8	-	99.6	156.6	119.1	134.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K3-532AXSP12	93.00	148.8	112.3	127	-	93.9	148.9	112.8	127.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K3-625AXSP12	104.80	164.3	125.1	140.9	-	105.7	164.4	125.8	141.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K3-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K4-425AXSP08	82.40	137.7	102.3	116.8	-	84.5	138.6	103.6	117.9	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K4-432AXSP08	76.00	128.5	95.1	108.9	225.1	78	129.3	96.3	109.7	224.7	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K4-525AXSP12	98.70	156.6	118.7	133.8	-	99.6	156.6	119.1	134.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K4-532AXSP12	93.00	148.8	112.3	127	-	93.9	148.9	112.8	127.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K4-625AXSP12	104.80	164.3	125.1	140.9	-	105.7	164.4	125.8	141.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K4-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K5-425AXSP08	82.40	137.7	102.3	116.8	-	84.5	138.6	103.6	117.9	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K5-432AXSP08	76.00	128.5	95.1	108.9	225.1	78	129.3	96.3	109.7	224.7	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K5-525AXSP12	98.70	156.6	118.7	133.8	-	99.6	156.6	119.1	134.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K5-532AXSP12	93.00	148.8	112.3	127	-	93.9	148.9	112.8	127.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K5-625AXSP12	104.80	164.3	125.1	140.9	-	105.7	164.4	125.8	141.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K5-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K8-425AXSP08	82.40	137.7	102.3	116.8	-	84.5	138.6	103.6	117.9	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K8-432AXSP08	76.00	128.5	95.1	108.9	225.1	78	129.3	96.3	109.7	224.7	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K8-525AXSP12	98.70	156.6	118.7	133.8	-	99.6	156.6	119.1	134.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K8-532AXSP12	93.00	148.8	112.3	127	-	93.9	148.9	112.8	127.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K8-625AXSP12	104.80	164.3	125.1	140.9	-	105.7	164.4	125.8	141.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K8-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-425AXSP08	82.40	137.7	102.3	116.8	-	84.5	138.6	103.6	117.9	-	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K9-432AXSP08	76.00	128.5	95.1	108.9	225.1	78	129.3	96.3	109.7	224.7	135	15.4	3"	108	14	2"	162	21.6	3"
EAW-FD1552PB750K9-525AXSP12	98.70	156.6	118.7	133.8	-	99.6	156.6	119.1	134.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K9-532AXSP12	93.00	148.8	112.3	127	-	93.9	148.9	112.8	127.2	-	113	26.1	2"	90	17.2	2"	135	30.8	3"
EAW-FD1552PB750K9-625AXSP12	104.80	164.3	125.1	140.9	-	105.7	164.4	125.8	141.1	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00	158.3	120.1	135.5	-	101	158.4	120.6	135.8	-	135	22.4	3"	108	18.6	2"	162	31.4	3"
EAW-FD1552PB750K9-632AXSP12	100.00																		

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S2ZB370K4-425AXSP12	85.10	135.7	102.7	116	-	85.6	135.4	102.7	115.9	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB370K4-432AXSP12	79.00	126.9	95.7	108.4	-	79.6	126.7	95.7	108.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB370K4-525AXSP12	92.70	146.4	111.2	125.4	-	93.3	145.8	111.2	125	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB370K4-532AXSP12	87.30	138.9	105.2	118.8	-	87.9	138.4	105.2	118.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB370K4-625AXSP12	100.10	156	119.3	134	-	100.8	155.4	119.3	133.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB370K4-632AXSP12	95.50	150.5	114.6	129	251.6	96.1	150	114.6	128.7	249.4	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB370K5-425AXSP12	85.10	135.7	102.7	116	-	85.6	135.4	102.7	115.9	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB370K5-432AXSP12	79.00	126.9	95.7	108.4	-	79.6	126.7	95.7	108.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB370K5-525AXSP12	92.70	146.4	111.2	125.4	-	93.3	145.8	111.2	125	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB370K5-532AXSP12	87.30	138.9	105.2	118.8	-	87.9	138.4	105.2	118.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB370K5-625AXSP12	100.10	156	119.3	134	-	100.8	155.4	119.3	133.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB370K5-632AXSP12	95.50	150.5	114.6	129	251.6	96.1	150	114.6	128.7	249.4	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB370K8-425AXSP12	85.10	135.7	102.7	116	-	85.6	135.4	102.7	115.9	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB370K8-432AXSP12	79.00	126.9	95.7	108.4	-	79.6	126.7	95.7	108.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB370K8-525AXSP12	92.70	146.4	111.2	125.4	-	93.3	145.8	111.2	125	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB370K8-532AXSP12	87.30	138.9	105.2	118.8	-	87.9	138.4	105.2	118.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB370K8-625AXSP12	100.10	156	119.3	134	-	100.8	155.4	119.3	133.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB370K8-632AXSP12	95.50	150.5	114.6	129	251.6	96.1	150	114.6	128.7	249.4	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400K3-425AXSP12	84.60	134.9	101.9	115.4	-	85.3	134.9	102.3	115.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400K3-432AXSP12	78.90	126.8	95.5	108.2	-	79.6	126.6	95.7	108.2	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400K3-525AXSP12	91.20	143.7	109.3	123.1	-	92	143.7	109.6	123.2	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400K3-532AXSP12	86.50	137.6	104.2	117.7	-	87.3	137.5	104.5	117.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400K3-625AXSP08	-	-	-	-	-	-	-	-	-	-	225	17.9	3"	180	11.8	3"	270	21.4	4"
EAW-FD15S2ZB400K3-632AXSP12	93.80	147.8	112.5	126.7	247	94.7	147.6	112.9	126.7	245.3	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400C3-425AXSP12	87.50	140	105.7	119.5	-	88.2	139.6	105.9	119.4	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400C3-432AXSP12	81.40	131	98.6	111.7	-	82	130.6	98.7	111.6	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400C3-525AXSP12	94.80	149.8	113.7	128.2	-	95.6	149.6	114	128.2	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400C3-532AXSP12	89.60	142.8	108	122.1	-	90.4	142.6	108.3	122.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400C3-625AXSP12	101.70	158.3	121.2	135.9	-	102.6	158.1	121.4	136.1	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400C3-632AXSP12	97.70	153.8	117.2	131.9	-	98.5	153.7	117.4	131.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400C9-425AXSP12	87.50	140	105.7	119.5	-	88.2	139.6	105.9	119.4	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400C9-432AXSP12	81.40	131	98.6	111.7	-	82	130.6	98.7	111.6	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400C9-525AXSP12	94.80	149.8	113.7	128.2	-	95.6	149.6	114	128.2	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400C9-532AXSP12	89.60	142.8	108	122.1	-	90.4	142.6	108.3	122.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400C9-625AXSP12	101.70	158.3	121.2	135.9	-	102.6	158.1	121.4	136.1	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400C9-632AXSP12	97.70	153.8	117.2	131.9	-	98.5	153.7	117.4	131.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400K3-425AXSP12	85.10	135.7	102.7	116	-	85.6	135.4	102.7	115.9	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400K3-432AXSP12	79.00	126.9	95.7	108.4	-	79.6	126.7	95.7	108.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400K3-525AXSP12	92.70	146.4	111.2	125.4	-	93.3	145.8	111.2	125	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400K3-532AXSP12	87.30	138.9	105.2	118.8	-	87.9	138.4	105.2	118.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400K3-625AXSP12	100.10	156	119.3	134	-	100.8	155.4	119.3	133.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400K3-632AXSP12	95.50	150.5	114.6	129	251.6	96.1	150	114.6	128.7	249.4	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400K9-425AXSP12	85.10	135.7	102.7	116	-	85.6	135.4	102.7	115.9	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400K9-432AXSP12	79.00	126.9	95.7	108.4	-	79.6	126.7	95.7	108.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400K9-525AXSP12	92.70	146.4	111.2	125.4	-	93.3	145.8	111.2	125	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400K9-532AXSP12	87.30	138.9	105.2	118.8	-	87.9	138.4	105.2	118.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400K9-625AXSP12	100.10	156	119.3	134	-	100.8	155.4	119.3	133.8	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400K9-632AXSP12	95.50	150.5	114.6	129	251.6	96.1	150	114.6	128.7	249.4	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400R3-425AXSP12	86.10	137.4	103.9	117.4	-	86.6	137.1	103.9	117.3	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400R3-432AXSP12	80.00	128.6	96.8	109.8	-	80.5	128.4	97	109.6	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB400R3-525AXSP12	93.70	148	112.4	126.7	-	94.4	147.5	112.6	126.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400R3-532AXSP12	88.20	140.5	106.3	120.2	-	88.9	140.1	106.5	120	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB400R3-625AXSP12	101.20	157.5	120.6	135.5	-	101.8	157.1	120.7	135.1	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB400R3-632AXSP12	96.50	152.1	115.8	130.5	-	97.3	151.7	115.9	130.1	252.4	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB550B3-425AXSP08	83.00	139	103.4	117.9	241.2	85.1	139.8	104.7	118.9	240.4	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD15S2ZB550B3-432AXSP12	84.80	136.5	102.7	116.4	-	85.5	136.5	103	116.5	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD15S2ZB550B3-525AXSP12	97.90	154.8	117.6	132.6	-	99	155	118.1	132.7	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB550B3-532AXSP12	92.80	148.1	112	126.7	-	93.7	148	112.4	126.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB550B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	225	17.9	3"	180	11.8	3"	270	21.4	4"
EAW-FD15S2ZB550B3-632AXSP12	-	-	-	-	-	101.8	158.9	121.4	136.4	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB550C2-425AXSP08	88.70	148.3	110.2	125.9	-	90.8	149.1	111.4	126.8	-	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD15S2ZB550C2-432AXSP08	81.60	138.1	102.3	117.1	241.5	83.6	138.7	103.4	117.8	240.5	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD15S2ZB550C2-525AXSP12	105.20	166.8	126.4	142.8	-	106.2	166.8	127	143.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB550C2-532AXSP12	99.00	158.2	119.5	135.1	-	99.8	158	119.7	135.3	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD15S2ZB550C2-625AXSP12	113.30	177.3	135.2	152.2	-	114.3	177.3	135.7	152.3	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD15S2ZB550C2-632AXSP12	108.30	171.3	130	146.6	-	109.3	171.2	130.4	146.7	-	152	22.8	3"	122	15.1	3"	183	32	3"

EAW-FD1552ZB550K2-632AXSP12	104.30	164.6	125.1	141	-	105.1	164.1	125.4	140.9	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K3-425AXSP08	84.70	141.9	105.6	120.6	246.5	86.8	142.7	106.7	121.2	245.5	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB550K3-432AXSP12	86.00	138.6	104.3	118.2	-	86.7	138.5	104.4	118.2	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD1552ZB550K3-525AXSP12	101.20	160.1	121.6	137.1	-	102	160	121.8	137.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K3-532AXSP12	95.00	151.6	114.7	129.5	-	95.7	151.4	114.8	129.5	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K3-625AXSP12	109.30	170.8	130.4	146.7	-	110.2	170.4	130.7	146.5	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K3-632AXSP12	104.30	164.6	125.1	141	-	105.1	164.1	125.4	140.9	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K4-425AXSP08	84.70	141.9	105.6	120.6	246.5	86.8	142.7	106.7	121.2	245.5	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB550K4-432AXSP12	86.00	138.6	104.3	118.2	-	86.7	138.5	104.4	118.2	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD1552ZB550K4-525AXSP12	101.20	160.1	121.6	137.1	-	102	160	121.8	137.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K4-532AXSP12	95.00	151.6	114.7	129.5	-	95.7	151.4	114.8	129.5	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K4-625AXSP12	109.30	170.8	130.4	146.7	-	110.2	170.4	130.7	146.5	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K4-632AXSP12	104.30	164.6	125.1	141	-	105.1	164.1	125.4	140.9	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K5-425AXSP08	84.70	141.9	105.6	120.6	246.5	86.8	142.7	106.7	121.2	245.5	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB550K5-432AXSP12	86.00	138.6	104.3	118.2	-	86.7	138.5	104.4	118.2	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD1552ZB550K5-525AXSP12	101.20	160.1	121.6	137.1	-	102	160	121.8	137.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K5-532AXSP12	95.00	151.6	114.7	129.5	-	95.7	151.4	114.8	129.5	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K5-625AXSP12	109.30	170.8	130.4	146.7	-	110.2	170.4	130.7	146.5	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K5-632AXSP12	104.30	164.6	125.1	141	-	105.1	164.1	125.4	140.9	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K8-425AXSP08	84.70	141.9	105.6	120.6	246.5	86.8	142.7	106.7	121.2	245.5	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB550K8-432AXSP12	86.00	138.6	104.3	118.2	-	86.7	138.5	104.4	118.2	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD1552ZB550K8-525AXSP12	101.20	160.1	121.6	137.1	-	102	160	121.8	137.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K8-532AXSP12	95.00	151.6	114.7	129.5	-	95.7	151.4	114.8	129.5	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K8-625AXSP12	109.30	170.8	130.4	146.7	-	110.2	170.4	130.7	146.5	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K8-632AXSP12	104.30	164.6	125.1	141	-	105.1	164.1	125.4	140.9	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K9-425AXSP08	84.70	141.9	105.6	120.6	246.5	86.8	142.7	106.7	121.2	245.5	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB550K9-432AXSP12	86.00	138.6	104.3	118.2	-	86.7	138.5	104.4	118.2	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD1552ZB550K9-525AXSP12	101.20	160.1	121.6	137.1	-	102	160	121.8	137.1	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K9-532AXSP12	95.00	151.6	114.7	129.5	-	95.7	151.4	114.8	129.5	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550K9-625AXSP12	109.30	170.8	130.4	146.7	-	110.2	170.4	130.7	146.5	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550K9-632AXSP12	104.30	164.6	125.1	141	-	105.1	164.1	125.4	140.9	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550R3-425AXSP08	86.40	144.6	107.6	122.8	251.6	88.5	145.6	108.8	123.6	250.3	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB550R3-432AXSP12	87.60	141.3	106.2	120.4	-	88.3	141.3	106.5	120.5	-	101	25.2	2"	81	16.6	2"	122	30.5	3"
EAW-FD1552ZB550R3-525AXSP12	103.10	163.2	123.9	139.9	-	103.9	163	124.1	139.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550R3-532AXSP12	96.80	154.5	116.7	132	-	97.5	154.3	116.9	132	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB550R3-625AXSP12	111.20	173.9	132.9	149.3	-	112.1	173.8	133	149.3	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB550R3-632AXSP12	106.10	167.6	127.5	143.7	-	107	167.3	127.7	143.6	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K2-425AXSP08	89.70	150.1	111.4	127.3	-	91.9	150.9	112.7	128.3	-	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K2-432AXSP08	82.70	139.7	103.5	118.5	244.9	84.7	140.6	104.8	119.3	243.6	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K2-525AXSP12	106.40	168.8	127.9	144.5	-	107.5	169	128.5	144.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K2-532AXSP12	100.10	160.1	120.8	136.6	-	100.9	159.9	121.1	136.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K2-625AXSP12	114.60	179.8	137.1	154.2	-	115.7	179.7	137.4	154.3	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K2-632AXSP12	109.50	173.3	131.5	148.3	-	110.5	173	131.9	148.4	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K3-425AXSP08	89.70	150.1	111.4	127.3	-	91.9	150.9	112.7	128.3	-	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K3-432AXSP08	82.70	139.7	103.5	118.5	244.9	84.7	140.6	104.8	119.3	243.6	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K3-525AXSP12	106.40	168.8	127.9	144.5	-	107.5	169	128.5	144.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K3-532AXSP12	100.10	160.1	120.8	136.6	-	100.9	159.9	121.1	136.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K3-625AXSP12	114.60	179.8	137.1	154.2	-	115.7	179.7	137.4	154.3	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K3-632AXSP12	109.50	173.3	131.5	148.3	-	110.5	173	131.9	148.4	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K4-425AXSP08	89.70	150.1	111.4	127.3	-	91.9	150.9	112.7	128.3	-	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K4-432AXSP08	82.70	139.7	103.5	118.5	244.9	84.7	140.6	104.8	119.3	243.6	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K4-525AXSP12	106.40	168.8	127.9	144.5	-	107.5	169	128.5	144.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K4-532AXSP12	100.10	160.1	120.8	136.6	-	100.9	159.9	121.1	136.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K4-625AXSP12	114.60	179.8	137.1	154.2	-	115.7	179.7	137.4	154.3	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K4-632AXSP12	109.50	173.3	131.5	148.3	-	110.5	173	131.9	148.4	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K5-425AXSP08	89.70	150.1	111.4	127.3	-	91.9	150.9	112.7	128.3	-	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K5-432AXSP08	82.70	139.7	103.5	118.5	244.9	84.7	140.6	104.8	119.3	243.6	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K5-525AXSP12	106.40	168.8	127.9	144.5	-	107.5	169	128.5	144.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K5-532AXSP12	100.10	160.1	120.8	136.6	-	100.9	159.9	121.1	136.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K5-625AXSP12	114.60	179.8	137.1	154.2	-	115.7	179.7	137.4	154.3	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K5-632AXSP12	109.50	173.3	131.5	148.3	-	110.5	173	131.9	148.4	-	152	22.8	3"	122	15.1	3"	183	32	3"
EAW-FD1552ZB750K8-425AXSP08	89.70	150.1	111.4	127.3	-	91.9	150.9	112.7	128.3	-	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K8-432AXSP08	82.70	139.7	103.5	118.5	244.9	84.7	140.6	104.8	119.3	243.6	152	15.8	3"	122	10.4	3"	183	22.1	3"
EAW-FD1552ZB750K8-525AXSP12	106.40	168.8	127.9	144.5	-	107.5	169	128.5	144.6	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K8-532AXSP12	100.10	160.1	120.8	136.6	-	100.9	159.9	121.1	136.8	-	124	22.2	3"	99	18	2"	149	31.1	3"
EAW-FD1552ZB750K8-625AXSP12	114.60	179.8	137.1	154.2	-	115.7													

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1552ZK370C8-625AXSP12	111.30	172.3	132.1	148.2	-	112	171.6	132.1	147.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370C8-632AXSP12	106.90	167	127.5	143.2	-	107.4	166.3	127.4	142.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K2-425AXSP08	85.20	140.4	105	119.5	241	86.6	140.3	105.7	119.6	239.1	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK370K2-432AXSP12	85.50	136.4	103.1	116.7	-	85.8	135.7	103	116.2	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK370K2-525AXSP12	100.70	157.5	120.2	135.1	-	100.9	156.7	120	134.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K2-532AXSP12	94.60	149.4	113.7	128	-	94.9	148.7	113.3	127.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K2-625AXSP12	108.80	168	129.1	144.7	-	109.1	167.2	128.7	143.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K2-632AXSP12	103.90	162	123.9	139.1	-	104.2	161.1	123.6	138.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K4-425AXSP08	85.20	140.4	105	119.5	241	86.6	140.3	105.7	119.6	239.1	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK370K4-432AXSP12	85.50	136.4	103.1	116.7	-	85.8	135.7	103	116.2	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK370K4-525AXSP12	100.70	157.5	120.2	135.1	-	100.9	156.7	120	134.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K4-532AXSP12	94.60	149.4	113.7	128	-	94.9	148.7	113.3	127.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K4-625AXSP12	108.80	168	129.1	144.7	-	109.1	167.2	128.7	143.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K4-632AXSP12	103.90	162	123.9	139.1	-	104.2	161.1	123.6	138.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K5-425AXSP08	85.20	140.4	105	119.5	241	86.6	140.3	105.7	119.6	239.1	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK370K5-432AXSP12	85.50	136.4	103.1	116.7	-	85.8	135.7	103	116.2	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK370K5-525AXSP12	100.70	157.5	120.2	135.1	-	100.9	156.7	120	134.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K5-532AXSP12	94.60	149.4	113.7	128	-	94.9	148.7	113.3	127.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K5-625AXSP12	108.80	168	129.1	144.7	-	109.1	167.2	128.7	143.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K5-632AXSP12	103.90	162	123.9	139.1	-	104.2	161.1	123.6	138.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K8-425AXSP08	85.20	140.4	105	119.5	241	86.6	140.3	105.7	119.6	239.1	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK370K8-432AXSP12	85.50	136.4	103.1	116.7	-	85.8	135.7	103	116.2	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK370K8-532AXSP12	100.70	157.5	120.2	135.1	-	100.9	156.7	120	134.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K8-532AXSP12	94.60	149.4	113.7	128	-	94.9	148.7	113.3	127.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK370K8-625AXSP12	108.80	168	129.1	144.7	-	109.1	167.2	128.7	143.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK370K8-632AXSP12	103.90	162	123.9	139.1	-	104.2	161.1	123.6	138.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400B3-425AXSP08	85.10	140.2	104.9	119.3	241	86.6	140.5	105.6	119.7	239.3	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400B3-432AXSP12	85.80	136.9	103.4	117.1	-	86.2	136.4	103.4	116.8	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK400B3-525AXSP12	99.80	156.1	119.2	133.9	-	100.3	155.7	119	133.7	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400B3-532AXSP12	94.40	149.1	113.2	127.8	-	94.9	148.6	113.3	127.3	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400B3-625AXSP12	106.80	165	126.7	142	-	107.5	164.4	126.7	141.7	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400B3-632AXSP12	102.90	160.5	122.7	138	-	103.5	160	122.7	137.4	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400C3-425AXSP08	88.10	145	108.5	123.5	249.4	89.6	145.2	109.2	123.8	247.8	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400C3-432AXSP08	81.40	135.5	101	115.2	234.5	82.9	135.6	101.7	115.4	232.7	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400C3-525AXSP12	103.50	162.2	123.8	139.3	-	104.1	161.7	123.6	138.9	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400C3-532AXSP12	97.60	154.4	117.3	132.2	-	98.1	153.9	117.1	131.9	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400C3-625AXSP12	111.30	172.3	132.1	148.2	-	112	171.6	132.1	147.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400C3-632AXSP12	106.90	167	127.5	143.2	-	107.4	166.3	127.4	142.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400C9-425AXSP08	88.10	145	108.5	123.5	249.4	89.6	145.2	109.2	123.8	247.8	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400C9-432AXSP08	81.40	135.5	101	115.2	234.5	82.9	135.6	101.7	115.4	232.7	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400C9-525AXSP12	103.50	162.2	123.8	139.3	-	104.1	161.7	123.6	138.9	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400C9-532AXSP12	97.60	154.4	117.3	132.2	-	98.1	153.9	117.1	131.9	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400C9-625AXSP12	111.30	172.3	132.1	148.2	-	112	171.6	132.1	147.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400C9-632AXSP12	106.90	167	127.5	143.2	-	107.4	166.3	127.4	142.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400K3-425AXSP08	85.20	140.4	105	119.5	241	86.6	140.3	105.7	119.6	239.1	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400K3-432AXSP12	85.50	136.4	103.1	116.7	-	85.8	135.7	103	116.2	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK400K3-525AXSP12	100.70	157.5	120.2	135.1	-	100.9	156.7	120	134.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400K3-532AXSP12	94.60	149.4	113.7	128	-	94.9	148.7	113.3	127.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400K3-625AXSP12	108.80	168	129.1	144.7	-	109.1	167.2	128.7	143.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400K3-632AXSP12	103.90	162	123.9	139.1	-	104.2	161.1	123.6	138.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400K9-425AXSP08	85.20	140.4	105	119.5	241	86.6	140.3	105.7	119.6	239.1	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400K9-525AXSP12	85.50	136.4	103.1	116.7	-	85.8	135.7	103	116.2	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK400K9-532AXSP12	100.70	157.5	120.2	135.1	-	100.9	156.7	120	134.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400K9-625AXSP12	94.60	149.4	113.7	128	-	94.9	148.7	113.3	127.6	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400K9-632AXSP12	108.80	168	129.1	144.7	-	109.1	167.2	128.7	143.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400R3-425AXSP08	86.30	142.2	106.5	121.2	244.6	87.9	142.2	107	121.4	242.5	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK400R3-432AXSP12	86.70	138.2	104.5	118.2	-	87	137.8	104.4	117.7	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK400R3-525AXSP12	101.90	159.5	121.7	136.8	-	102.1	158.8	121.5	136.3	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400R3-532AXSP12	95.80	151.4	114.9	129.7	-	96.2	150.8	114.9	129.3	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK400R3-625AXSP12	110.00	170.2	130.5	146.3	-	110.4	169.2	130.2	145.7	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK400R3-632AXSP12	105.10	164.1	125.4	140.8	-	105.5	163.2	125.1	140.4	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK50B3-425AXSP08	92.30	151.6	113.4	128.9	-	94	152.2	114.3	129.6	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK50B3-432AXSP12	85.40	141.9	105.8	120.6	246.3	87	142.3	106.6	121.1	244.9	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK50B3-525AXSP12	107.60	169	128.8	144.9	-	108.3	168.8	128.9	144.7	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK50B3-532AXSP12	101.80	161.3	122.2	137.9	-	102.4	160.9	122.4	137.7	-	124								

EAW-FD1552ZK550C9-532AXSP12	108.10	171.6	129.9	146.7	-	108.6	171	129.9	146.4	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550C9-625AXSP12	124.40	193.3	147.9	166	-	125.2	192.9	148	165.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550C9-632AXSP12	118.70	186.3	141.9	159.6	-	119.3	185.5	142	159.4	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K2-425AXSP08	93.70	154	115.1	131.2	-	95.3	154.3	115.9	131.4	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K2-432AXSP08	86.30	143.5	106.9	121.9	248.9	87.9	143.8	107.6	122.3	247.2	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K2-525AXSP12	110.10	173.2	131.9	148.5	-	110.8	172.6	131.7	148.2	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K2-532AXSP12	103.40	164	124.4	140.4	-	104	163.3	124.4	140	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K2-625AXSP12	119.20	185.1	141.9	159.2	-	119.8	184.3	141.7	158.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K2-632AXSP12	113.70	177.9	135.7	152.8	-	114.2	177.2	135.6	152.1	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K3-425AXSP08	93.70	154	115.1	131.2	-	95.3	154.3	115.9	131.4	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K3-432AXSP08	86.30	143.5	106.9	121.9	248.9	87.9	143.8	107.6	122.3	247.2	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K3-525AXSP12	110.10	173.2	131.9	148.5	-	110.8	172.6	131.7	148.2	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K3-532AXSP12	103.40	164	124.4	140.4	-	104	163.3	124.4	140	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K3-625AXSP12	119.20	185.1	141.9	159.2	-	119.8	184.3	141.7	158.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K3-632AXSP12	113.70	177.9	135.7	152.8	-	114.2	177.2	135.6	152.1	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K3-425AXSP08	93.70	154	115.1	131.2	-	95.3	154.3	115.9	131.4	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K4-432AXSP08	86.30	143.5	106.9	121.9	248.9	87.9	143.8	107.6	122.3	247.2	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K4-525AXSP12	110.10	173.2	131.9	148.5	-	110.8	172.6	131.7	148.2	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K4-532AXSP12	103.40	164	124.4	140.4	-	104	163.3	124.4	140	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K4-625AXSP12	119.20	185.1	141.9	159.2	-	119.8	184.3	141.7	158.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K4-632AXSP12	113.70	177.9	135.7	152.8	-	114.2	177.2	135.6	152.1	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K5-425AXSP08	93.70	154	115.1	131.2	-	95.3	154.3	115.9	131.4	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K5-432AXSP08	86.30	143.5	106.9	121.9	248.9	87.9	143.8	107.6	122.3	247.2	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K5-525AXSP12	110.10	173.2	131.9	148.5	-	110.8	172.6	131.7	148.2	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K5-532AXSP12	103.40	164	124.4	140.4	-	104	163.3	124.4	140	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K5-625AXSP12	119.20	185.1	141.9	159.2	-	119.8	184.3	141.7	158.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K5-632AXSP12	113.70	177.9	135.7	152.8	-	114.2	177.2	135.6	152.1	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K8-425AXSP08	93.70	154	115.1	131.2	-	95.3	154.3	115.9	131.4	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K8-432AXSP08	86.30	143.5	106.9	121.9	248.9	87.9	143.8	107.6	122.3	247.2	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K8-525AXSP12	110.10	173.2	131.9	148.5	-	110.8	172.6	131.7	148.2	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K8-532AXSP12	103.40	164	124.4	140.4	-	104	163.3	124.4	140	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K8-625AXSP12	119.20	185.1	141.9	159.2	-	119.8	184.3	141.7	158.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K8-632AXSP12	113.70	177.9	135.7	152.8	-	114.2	177.2	135.6	152.1	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K9-425AXSP08	93.70	154	115.1	131.2	-	95.3	154.3	115.9	131.4	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K9-432AXSP08	86.30	143.5	106.9	121.9	248.9	87.9	143.8	107.6	122.3	247.2	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550K9-525AXSP12	110.10	173.2	131.9	148.5	-	110.8	172.6	131.7	148.2	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K9-532AXSP12	103.40	164	124.4	140.4	-	104	163.3	124.4	140	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550K9-625AXSP12	119.20	185.1	141.9	159.2	-	119.8	184.3	141.7	158.6	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550K9-632AXSP12	113.70	177.9	135.7	152.8	-	114.2	177.2	135.6	152.1	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550R3-425AXSP08	95.70	157.3	117.4	133.6	-	97.4	157.5	118.4	134.2	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550R3-432AXSP08	88.20	146.5	109	124.4	-	89.7	146.7	109.8	124.8	252.5	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK550R3-525AXSP08	103.80	169.8	127.7	144.9	289.9	105.8	170.3	128.6	145.5	288.2	186	18	3"	149	11.9	3"	223	25.3	3"
EAW-FD1552ZK550R3-532AXSP12	105.40	167.2	126.9	143	-	106.1	166.8	126.7	142.9	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK550R3-625AXSP12	121.60	188.9	144.7	162.4	-	122.2	188.2	144.5	161.9	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK550R3-632AXSP12	115.90	181.5	138.4	155.9	-	116.5	180.9	138.4	155.3	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK750C4-425AXSP12	110.10	-	132.6	149.8	-	110.7	-	132.9	149.9	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK750C4-432AXSP12	101.80	163.6	123.2	139.4	-	102.5	163.2	123.4	139.4	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK750C4-525AXSP12	119.70	188.6	143.3	161.6	-	120.4	188.4	143.6	161.5	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK750C4-532AXSP12	112.50	178.7	135.5	152.9	-	113.2	178.4	135.6	152.8	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK750C4-632AXSP12	123.10	193.6	147.2	166	-	124	193.2	147.4	165.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK750C5-425AXSP12	110.10	-	132.6	149.8	-	110.7	-	132.9	149.9	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK750C5-432AXSP12	101.80	163.6	123.2	139.4	-	102.5	163.2	123.4	139.4	-	101	27.2	2"	81	17.9	2"	122	33.3	3"
EAW-FD1552ZK750C5-525AXSP12	119.70	188.6	143.3	161.6	-	120.4	188.4	143.6	161.5	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK750C5-532AXSP12	112.50	178.7	135.5	152.9	-	113.2	178.4	135.6	152.8	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK750C5-632AXSP12	123.10	193.6	147.2	166	-	124	193.2	147.4	165.8	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK750K2-425AXSP08	99.50	163.3	122	139	-	101.3	164	123	139.6	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK750K2-432AXSP08	91.80	152.3	113.3	129.3	-	93.5	152.6	114.2	129.8	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK750K2-525AXSP08	108.00	176.3	132.6	150.5	301.4	109.9	176.9	133.4	151	299.6	186	18	3"	149	11.9	3"	223	25.3	3"
EAW-FD1552ZK750K2-532AXSP12	109.40	173.6	131.6	148.7	-	110.1	173.2	131.8	148.5	-	124	24.1	3"	99	19.3	2"	149	33.9	3"
EAW-FD1552ZK750K2-625AXSP12	125.90	195.8	149.7	168.1	-	126.7	195.5	150	168	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK750K2-632AXSP12	120.10	188.3	143.6	161.6	-	120.7	187.9	143.5	161.3	-	152	24.8	3"	122	16.4	3"	183	34.7	3"
EAW-FD1552ZK750K3-425AXSP08	99.50	163.3	122	139	-	101.3	164	123	139.6	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK750K3-432AXSP08	91.80	152.3	113.3	129.3	-	93.5	152.6	114.2	129.8	-	152	17.1	3"	122	11.3	3"	183	24	3"
EAW-FD1552ZK750K3-525AXSP08	108.00	176.3	132.6	150.5	301.4	109.9	176.9	133.4	151	299.6	186	18	3"	149	11.9	3"	223	25.3	3"
EAW-FD1552ZK750K3-532AXSP12	109.40	173.6	131.6	148.7	-	110.1	173.2	131.8	148.5	-	124</								

EAW-FD1553PB370C2-625AXSP08	138.40	215.8	165	185.5	-	139.7	216.1	165.7	185.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370C2-632AXSP08	133.40	210.5	160.2	180.4	-	134.9	210.6	160.8	180.7	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370C4-425AXSP06	113.70	186.7	139.5	158.9	-	115.9	187.4	140.8	159.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD1553PB370C4-432AXSP08	112.10	180.6	136	154.2	-	113.1	180.6	136.3	154.2	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370C4-525AXSP08	131.50	207.6	157.8	177.9	-	132.7	207.8	158.6	178.3	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370C4-532AXSP08	124.80	198.8	150.5	169.9	-	126	198.9	150.9	170.2	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370C4-625AXSP08	138.40	215.8	165	185.5	-	139.7	216.1	165.7	185.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370C5-425AXSP06	113.70	186.7	139.5	158.9	-	115.9	187.4	140.8	159.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD1553PB370C5-432AXSP08	112.10	180.6	136	154.2	-	113.1	180.6	136.3	154.2	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370C5-525AXSP08	131.50	207.6	157.8	177.9	-	132.7	207.8	158.6	178.3	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370C5-532AXSP08	124.80	198.8	150.5	169.9	-	126	198.9	150.9	170.2	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370C5-625AXSP08	138.40	215.8	165	185.5	-	139.7	216.1	165.7	185.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370C5-632AXSP08	133.40	210.5	160.2	180.4	-	134.9	210.6	160.8	180.7	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370C8-425AXSP06	113.70	186.7	139.5	158.9	-	115.9	187.4	140.8	159.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD1553PB370C8-432AXSP08	112.10	180.6	136	154.2	-	113.1	180.6	136.3	154.2	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370C8-525AXSP08	131.50	207.6	157.8	177.9	-	132.7	207.8	158.6	178.3	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370C8-532AXSP08	124.80	198.8	150.5	169.9	-	126	198.9	150.9	170.2	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370C8-625AXSP08	138.40	215.8	165	185.5	-	139.7	216.1	165.7	185.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370C8-632AXSP08	133.40	210.5	160.2	180.4	-	134.9	210.6	160.8	180.7	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K2-425AXSP08	117.80	188.1	142.3	160.9	-	118.6	187.9	142.4	160.6	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K2-432AXSP08	109.30	175.9	132.5	150.2	-	110.2	175.9	132.7	150.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K2-525AXSP08	129.80	205	155.7	175.5	-	130.7	204.6	155.9	175.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K2-532AXSP08	122.40	195.1	147.6	166.8	-	123.3	194.7	147.6	166.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K2-625AXSP08	138.00	215.4	164.7	184.9	-	139.1	215	164.7	184.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K2-632AXSP08	131.90	208	158.3	178.3	-	133	207.7	158.5	178	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K4-425AXSP08	117.80	188.1	142.3	160.9	-	118.6	187.9	142.4	160.6	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K4-432AXSP08	109.30	175.9	132.5	150.2	-	110.2	175.9	132.7	150.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K4-525AXSP08	129.80	205	155.7	175.5	-	130.7	204.6	155.9	175.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K4-532AXSP08	122.40	195.1	147.6	166.8	-	123.3	194.7	147.6	166.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K4-625AXSP08	138.00	215.4	164.7	184.9	-	139.1	215	164.7	184.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K4-632AXSP08	131.90	208	158.3	178.3	-	133	207.7	158.5	178	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K5-425AXSP08	117.80	188.1	142.3	160.9	-	118.6	187.9	142.4	160.6	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K5-432AXSP08	109.30	175.9	132.5	150.2	-	110.2	175.9	132.7	150.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K5-525AXSP08	129.80	205	155.7	175.5	-	130.7	204.6	155.9	175.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K5-532AXSP08	122.40	195.1	147.6	166.8	-	123.3	194.7	147.6	166.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K5-625AXSP08	138.00	215.4	164.7	184.9	-	139.1	215	164.7	184.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K5-632AXSP08	131.90	208	158.3	178.3	-	133	207.7	158.5	178	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K8-425AXSP08	117.80	188.1	142.3	160.9	-	118.6	187.9	142.4	160.6	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K8-432AXSP08	109.30	175.9	132.5	150.2	-	110.2	175.9	132.7	150.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB370K8-525AXSP08	129.80	205	155.7	175.5	-	130.7	204.6	155.9	175.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K8-532AXSP08	122.40	195.1	147.6	166.8	-	123.3	194.7	147.6	166.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB370K8-625AXSP08	138.00	215.4	164.7	184.9	-	139.1	215	164.7	184.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB370K8-632AXSP08	131.90	208	158.3	178.3	-	133	207.7	158.5	178	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB400B3-425AXSP08	116.00	185.6	139.9	158.5	-	117.1	185.7	140.5	158.7	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB400B3-432AXSP08	108.50	174.5	131.5	149	-	109.5	174.6	131.9	149.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB400B3-525AXSP06	-	-	-	-	-	-	-	-	-	-	225	18.8	3"	180	12.4	3"	270	22.7	4"
EAW-FD1553PB400B3-532AXSP08	120.10	191.4	144.7	163.5	-	121.3	191.3	145.4	163.9	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	270	16.7	4"	216	13.5	3"	325	23.5	4"
EAW-FD1553PB400B3-632AXSP06	-	-	-	-	-	-	-	-	-	-	270	16.7	4"	216	13.5	3"	325	23.5	4"
EAW-FD1553PB400C3-425AXSP06	113.70	186.7	139.5	158.9	-	115.9	187.4	140.8	159.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD1553PB400C3-432AXSP08	112.10	180.6	136	154.2	-	113.1	180.6	136.3	154.2	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB400C3-525AXSP08	131.50	207.6	157.8	177.9	-	132.7	207.8	158.6	178.3	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400C3-532AXSP08	124.80	198.8	150.5	169.9	-	126	198.9	150.9	170.2	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400C3-625AXSP08	138.40	215.8	165	185.5	-	139.7	216.1	165.7	185.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB400C3-632AXSP08	133.40	210.5	160.2	180.4	-	134.9	210.6	160.8	180.7	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB400C9-425AXSP06	113.70	186.7	139.5	158.9	-	115.9	187.4	140.8	159.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD1553PB400C9-432AXSP08	112.10	180.6	136	154.2	-	113.1	180.6	136.3	154.2	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB400C9-525AXSP08	131.50	207.6	157.8	177.9	-	132.7	207.8	158.6	178.3	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400C9-532AXSP08	124.80	198.8	150.5	169.9	-	126	198.9	150.9	170.2	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400C9-625AXSP08	138.40	215.8	165	185.5	-	139.7	216.1	165.7	185.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB400C9-632AXSP08	133.40	210.5	160.2	180.4	-	134.9	210.6	160.8	180.7	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB400K3-425AXSP08	117.80	188.1	142.3	160.9	-	118.6	187.9	142.4	160.6	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB400K3-432AXSP08	109.30	175.9	132.5	150.2	-	110.2	175.9	132.7	150.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD1553PB400K3-525AXSP08	129.80	205	155.7	175.5	-	130.7	204.6	155.9	175.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400K3-532AXSP08	122.40	195.1	147.6	166.8	-	123.3	194.7	147.6	166.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD1553PB400K3-625AXSP08	138.00	215.4	164.7	184.9	-	139.1	215	164.7	184.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD1553PB400K3-632AXSP08	131.90	208	158.3	178.3	-	133	207.7	158.5	178	-	203	23							

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3PB550C4-632AXSP08	-	-	-	-	-	149.1	233.8	178	200.4	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550C5-425AXSP06	125.80	206.7	154.1	175.5	-	128.1	207.5	155.7	176.7	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550C5-432AXSP06	116.40	192.7	143.4	163.6	-	118.7	193.6	144.7	164.6	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550C5-525AXSP08	145.60	230.9	175.1	197.8	-	147.1	231.5	176.1	198.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550C5-532AXSP08	137.50	220	166	187.7	-	138.8	220.1	166.7	188.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550C5-632AXSP08	-	-	-	-	-	149.1	233.8	178	200.4	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550C8-425AXSP06	125.80	206.7	154.1	175.5	-	128.1	207.5	155.7	176.7	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550C8-432AXSP06	116.40	192.7	143.4	163.6	-	118.7	193.6	144.7	164.6	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550C8-525AXSP08	145.60	230.9	175.1	197.8	-	147.1	231.5	176.1	198.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550C8-532AXSP08	137.50	220	166	187.7	-	138.8	220.1	166.7	188.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550C8-632AXSP08	-	-	-	-	-	149.1	233.8	178	200.4	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550C9-425AXSP06	125.80	206.7	154.1	175.5	-	128.1	207.5	155.7	176.7	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550C9-432AXSP06	116.40	192.7	143.4	163.6	-	118.7	193.6	144.7	164.6	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550C9-525AXSP08	145.60	230.9	175.1	197.8	-	147.1	231.5	176.1	198.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550C9-532AXSP08	137.50	220	166	187.7	-	138.8	220.1	166.7	188.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550C9-625AXSP06	-	-	-	-	-	-	-	-	-	-	270	16.7	4"	216	13.5	3"	325	23.5	4"
EAW-FD15S3PB550C9-632AXSP08	-	-	-	-	-	149.1	233.8	178	200.4	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K2-425AXSP06	121.00	198.6	148.3	168.9	-	123.2	199.3	149.6	169.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550K2-432AXSP08	118.50	191.2	143.7	163	-	119.5	191.3	144.2	163.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD15S3PB550K2-525AXSP08	140.90	223.4	169.3	191.2	-	142	223	169.9	191.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K2-532AXSP08	132.70	212.1	160	181.2	-	134	211.7	160.7	181.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K2-625AXSP08	149.90	234.6	179.2	201.3	-	151.2	234.4	179.5	201.6	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K2-632AXSP08	143.10	226	171.7	193.7	-	144.3	226.2	172.2	193.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K3-425AXSP06	121.00	198.6	148.3	168.9	-	123.2	199.3	149.6	169.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550K3-432AXSP08	118.50	191.2	143.7	163	-	119.5	191.3	144.2	163.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD15S3PB550K3-525AXSP08	140.90	223.4	169.3	191.2	-	142	223	169.9	191.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K3-532AXSP08	132.70	212.1	160	181.2	-	134	211.7	160.7	181.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K3-625AXSP08	149.90	234.6	179.2	201.3	-	151.2	234.4	179.5	201.6	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K3-632AXSP08	143.10	226	171.7	193.7	-	144.3	226.2	172.2	193.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K4-425AXSP06	121.00	198.6	148.3	168.9	-	123.2	199.3	149.6	169.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550K4-432AXSP08	118.50	191.2	143.7	163	-	119.5	191.3	144.2	163.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD15S3PB550K4-525AXSP08	140.90	223.4	169.3	191.2	-	142	223	169.9	191.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K4-532AXSP08	132.70	212.1	160	181.2	-	134	211.7	160.7	181.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K4-625AXSP08	149.90	234.6	179.2	201.3	-	151.2	234.4	179.5	201.6	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K4-632AXSP08	143.10	226	171.7	193.7	-	144.3	226.2	172.2	193.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K5-425AXSP06	121.00	198.6	148.3	168.9	-	123.2	199.3	149.6	169.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550K5-432AXSP08	118.50	191.2	143.7	163	-	119.5	191.3	144.2	163.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD15S3PB550K5-525AXSP08	140.90	223.4	169.3	191.2	-	142	223	169.9	191.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K5-532AXSP08	132.70	212.1	160	181.2	-	134	211.7	160.7	181.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K5-625AXSP08	149.90	234.6	179.2	201.3	-	151.2	234.4	179.5	201.6	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K5-632AXSP08	143.10	226	171.7	193.7	-	144.3	226.2	172.2	193.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K8-425AXSP06	121.00	198.6	148.3	168.9	-	123.2	199.3	149.6	169.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550K8-432AXSP08	118.50	191.2	143.7	163	-	119.5	191.3	144.2	163.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD15S3PB550K8-525AXSP08	140.90	223.4	169.3	191.2	-	142	223	169.9	191.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K8-532AXSP08	132.70	212.1	160	181.2	-	134	211.7	160.7	181.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K8-625AXSP08	149.90	234.6	179.2	201.3	-	151.2	234.4	179.5	201.6	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K8-632AXSP08	143.10	226	171.7	193.7	-	144.3	226.2	172.2	193.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K9-425AXSP06	121.00	198.6	148.3	168.9	-	123.2	199.3	149.6	169.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550K9-432AXSP08	118.50	191.2	143.7	163	-	119.5	191.3	144.2	163.1	-	135	21.3	3"	108	17.9	2"	162	29.9	3"
EAW-FD15S3PB550K9-525AXSP08	140.90	223.4	169.3	191.2	-	142	223	169.9	191.4	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K9-532AXSP08	132.70	212.1	160	181.2	-	134	211.7	160.7	181.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550K9-625AXSP08	149.90	234.6	179.2	201.3	-	151.2	234.4	179.5	201.6	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550K9-632AXSP08	143.10	226	171.7	193.7	-	144.3	226.2	172.2	193.8	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550R3-425AXSP06	123.20	202.1	150.9	172	-	125.4	202.9	152.3	172.8	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550R3-432AXSP06	113.90	188.5	140.4	160	-	116	189.2	141.5	160.9	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB550R3-525AXSP08	143.10	227.2	172.4	194.3	-	144.6	227.3	172.8	194.6	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550R3-532AXSP08	134.90	215.6	162.9	184.1	-	136.2	215.5	163.4	184.6	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB550R3-625AXSP08	152.50	238.8	182	204.8	-	153.6	238.6	182.7	204.9	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB550R3-632AXSP08	145.50	230	174.7	197.1	-	146.8	229.9	175.3	197.2	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB750K2-425AXSP06	127.00	209	155.8	177.6	-	129.5	209.9	157.4	178.7	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB750K2-432AXSP06	117.70	194.7	145	165.4	-	119.9	195.7	146.3	166.3	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB750K2-525AXSP08	147.50	234.1	177.4	200.4	-	148.9	234.1	178	200.7	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB750K2-532AXSP08	138.90	222.4	167.7	189.7	-	140.4	222.6	168.5	190.1	-	169	22.1	3"	135	14.6	3"	203	31	3"
EAW-FD15S3PB750K2-625AXSP08	156.70	245.7	187.4	210.6	-	158.1	245.9	188.1	211	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB750K2-632AXSP08	149.40	236.7	179.8	202.6	-	151	236.9	180.3	203	-	203	23	3"	162	15.2	3"	244	32.4	3"
EAW-FD15S3PB750K3-425AXSP06	127.00	209	155.8	177.6	-	129.5	209.9	157.4	178.7	-	180	17.4	3"	144	11.5	3"	216	24.4	3"
EAW-FD15S3PB750K3																			

EAW-FD1553ZB370C2-425AXSP08	130.80	209.2	158	178.6	-	131.8	209	158.2	178.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C2-432AXSP08	121.70	195.7	147.3	167.1	-	122.6	195.6	147.6	166.9	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C2-525AXSP08	141.70	224	170	191.7	-	142.9	223.8	170.5	191.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C2-532AXSP08	133.90	213.6	161.4	182.5	-	135.1	213.2	161.8	182.5	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C2-625AXSP08	150.90	235.5	180.1	202.2	-	152.2	235.3	180.6	202.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C2-632AXSP08	145.00	228.6	173.8	196	-	146.3	228.2	174.4	195.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C2-425AXSP08	130.80	209.2	158	178.6	-	131.8	209	158.2	178.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C2-432AXSP08	121.70	195.7	147.3	167.1	-	122.6	195.6	147.6	166.9	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C2-525AXSP08	141.70	224	170	191.7	-	142.9	223.8	170.5	191.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C2-532AXSP08	133.90	213.6	161.4	182.5	-	135.1	213.2	161.8	182.5	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C2-625AXSP08	150.90	235.5	180.1	202.2	-	152.2	235.3	180.6	202.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C2-632AXSP08	145.00	228.6	173.8	196	-	146.3	228.2	174.4	195.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C5-432AXSP08	121.70	195.7	147.3	167.1	-	122.6	195.6	147.6	166.9	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C5-525AXSP08	141.70	224	170	191.7	-	142.9	223.8	170.5	191.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C5-532AXSP08	133.90	213.6	161.4	182.5	-	135.1	213.2	161.8	182.5	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C5-625AXSP08	150.90	235.5	180.1	202.2	-	152.2	235.3	180.6	202.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C5-632AXSP08	145.00	228.6	173.8	196	-	146.3	228.2	174.4	195.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C8-425AXSP08	130.80	209.2	158	178.6	-	131.8	209	158.2	178.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C8-432AXSP08	121.70	195.7	147.3	167.1	-	122.6	195.6	147.6	166.9	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370C8-525AXSP08	141.70	224	170	191.7	-	142.9	223.8	170.5	191.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C8-532AXSP08	133.90	213.6	161.4	182.5	-	135.1	213.2	161.8	182.5	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370C8-625AXSP08	150.90	235.5	180.1	202.2	-	152.2	235.3	180.6	202.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370C8-632AXSP08	145.00	228.6	173.8	196	-	146.3	228.2	174.4	195.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K2-432AXSP08	127.20	203.3	153.5	173.7	-	128.2	202.8	153.7	173.2	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K2-525AXSP08	118.00	190	143	162.1	-	118.9	189.3	143.1	161.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K2-532AXSP08	138.60	218.9	166.3	187.4	-	139.6	218.4	166.5	187.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K2-625AXSP08	130.40	207.6	157.2	177.6	-	131.4	207	157.3	177.3	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K2-632AXSP08	148.90	232.1	177.4	199.3	-	149.7	231.2	177.5	199	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K2-632AXSP08	141.60	223.8	170.2	191.7	374.5	142.8	222.8	170.4	191.3	370.8	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K4-425AXSP08	127.20	203.3	153.5	173.7	-	128.2	202.8	153.7	173.2	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K4-432AXSP08	118.00	190	143	162.1	-	118.9	189.3	143.1	161.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K4-525AXSP08	138.60	218.9	166.3	187.4	-	139.6	218.4	166.5	187.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K4-532AXSP08	130.40	207.6	157.2	177.6	-	131.4	207	157.3	177.3	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K4-625AXSP08	148.90	232.1	177.4	199.3	-	149.7	231.2	177.5	199	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K4-632AXSP08	141.60	223.8	170.2	191.7	374.5	142.8	222.8	170.4	191.3	370.8	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K5-432AXSP08	127.20	203.3	153.5	173.7	-	128.2	202.8	153.7	173.2	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K5-432AXSP08	118.00	190	143	162.1	-	118.9	189.3	143.1	161.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K5-525AXSP08	138.60	218.9	166.3	187.4	-	139.6	218.4	166.5	187.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K5-532AXSP08	130.40	207.6	157.2	177.6	-	131.4	207	157.3	177.3	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K5-625AXSP08	148.90	232.1	177.4	199.3	-	149.7	231.2	177.5	199	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K5-632AXSP08	141.60	223.8	170.2	191.7	374.5	142.8	222.8	170.4	191.3	370.8	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K8-425AXSP08	127.20	203.3	153.5	173.7	-	128.2	202.8	153.7	173.2	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K8-432AXSP08	118.00	190	143	162.1	-	118.9	189.3	143.1	161.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB370K8-525AXSP08	138.60	218.9	166.3	187.4	-	139.6	218.4	166.5	187.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K8-532AXSP08	130.40	207.6	157.2	177.6	-	131.4	207	157.3	177.3	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB370K8-625AXSP08	148.90	232.1	177.4	199.3	-	149.7	231.2	177.5	199	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB370K8-632AXSP08	141.60	223.8	170.2	191.7	374.5	142.8	222.8	170.4	191.3	370.8	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB400B3-425AXSP08	126.30	201.7	152.6	172.4	-	127.5	201.6	152.9	172.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB400B3-432AXSP08	117.90	189.5	142.8	161.7	-	118.8	189.2	143	161.8	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB400B3-525AXSP08	136.30	214.9	163.4	184.1	-	137.5	214.9	163.9	184.3	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB400B3-532AXSP08	129.20	206	155.7	175.9	-	130.5	205.5	156.2	176	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	304	17.2	4"	244	14.5	3"	365	24.2	4"
EAW-FD1553ZB400B3-632AXSP08	139.10	219.5	167.1	188.4	367.6	140.6	219.2	167.5	188.4	364.7	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB400C3-425AXSP08	130.80	209.2	158	178.6	-	131.8	209	158.2	178.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB400C3-432AXSP08	121.70	195.7	147.3	167.1	-	122.6	195.6	147.6	166.9	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB400C3-525AXSP08	141.70	224	170	191.7	-	142.9	223.8	170.5	191.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB400C3-532AXSP08	133.90	213.6	161.4	182.5	-	135.1	213.2	161.8	182.5	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB400C3-625AXSP08	150.90	235.5	180.1	202.2	-	152.2	235.3	180.6	202.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB400C3-632AXSP08	145.00	228.6	173.8	196	-	146.3	228.2	174.4	195.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB400C9-425AXSP08	130.80	209.2	158	178.6	-	131.8	209	158.2	178.7	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB400C9-432AXSP08	121.70	195.7	147.3	167.1	-	122.6	195.6	147.6	166.9	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB400C9-525AXSP08	141.70	224	170	191.7	-	142.9	223.8	170.5	191.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB400C9-532AXSP08	133.90	213.6	161.4	182.5	-	135.1	213.2	161.8	182.5	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB400C9-625AXSP08	150.90	235.5	180.1	202.2	-	152.2	235.3	180.6	202.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB400C9-632AXSP08	145.00	228.6	173.8	196	-	146.3	228.2	174.4	195.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB400K3-425AXSP08	127.20	203.3																	

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZB550C3-632AXSP08	160.70	254.2	193	217.7	-	162.2	254.1	193.6	217.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C4-425AXSP06	137.10	225	167.8	191.2	-	139.4	225.8	169.3	192	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550C4-432AXSP08	133.80	216.3	162.4	184.3	-	135	215.9	163	184.3	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550C4-525AXSP08	157.20	249.8	189.3	213.5	-	158.8	249.5	189.8	213.9	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C4-532AXSP08	147.90	236.5	178.5	202.2	-	149.3	236.6	179.3	202.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C4-625AXSP08	168.10	263.8	201	226.2	-	169.8	263.8	201.7	226.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C4-632AXSP08	160.70	254.2	193	217.7	-	162.2	254.1	193.6	217.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C5-425AXSP06	137.10	225	167.8	191.2	-	139.4	225.8	169.3	192	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550C5-432AXSP08	133.80	216.3	162.4	184.3	-	135	215.9	163	184.3	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550C5-525AXSP08	157.20	249.8	189.3	213.5	-	158.8	249.5	189.8	213.9	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C5-532AXSP08	147.90	236.5	178.5	202.2	-	149.3	236.6	179.3	202.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C5-625AXSP08	168.10	263.8	201	226.2	-	169.8	263.8	201.7	226.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C5-632AXSP08	160.70	254.2	193	217.7	-	162.2	254.1	193.6	217.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C8-425AXSP06	137.10	225	167.8	191.2	-	139.4	225.8	169.3	192	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550C8-432AXSP08	133.80	216.3	162.4	184.3	-	135	215.9	163	184.3	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550C8-525AXSP08	157.20	249.8	189.3	213.5	-	158.8	249.5	189.8	213.9	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C8-532AXSP08	147.90	236.5	178.5	202.2	-	149.3	236.6	179.3	202.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C8-625AXSP08	168.10	263.8	201	226.2	-	169.8	263.8	201.7	226.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C8-632AXSP08	160.70	254.2	193	217.7	-	162.2	254.1	193.6	217.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C9-425AXSP06	137.10	225	167.8	191.2	-	139.4	225.8	169.3	192	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550C9-432AXSP08	133.80	216.3	162.4	184.3	-	135	215.9	163	184.3	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550C9-525AXSP08	157.20	249.8	189.3	213.5	-	158.8	249.5	189.8	213.9	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C9-532AXSP08	147.90	236.5	178.5	202.2	-	149.3	236.6	179.3	202.2	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550C9-625AXSP08	168.10	263.8	201	226.2	-	169.8	263.8	201.7	226.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550C9-632AXSP08	160.70	254.2	193	217.7	-	162.2	254.1	193.6	217.9	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K2-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550K2-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550K2-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K2-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K2-625AXSP08	162.20	254.1	193.9	218.1	-	163.5	253.5	194.3	217.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K2-632AXSP08	154.80	244.6	185.7	209.4	-	155.8	244	185.9	209.1	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K3-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550K3-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550K3-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K3-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K3-625AXSP08	162.20	254.1	193.9	218.1	-	163.5	253.5	194.3	217.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K3-632AXSP08	154.80	244.6	185.7	209.4	-	155.8	244	185.9	209.1	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K4-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550K4-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550K4-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K4-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K4-625AXSP08	162.20	254.1	193.9	218.1	-	163.5	253.5	194.3	217.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K4-632AXSP08	154.80	244.6	185.7	209.4	-	155.8	244	185.9	209.1	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K5-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550K5-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550K5-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K5-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K5-625AXSP08	162.20	254.1	193.9	218.1	-	163.5	253.5	194.3	217.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K5-632AXSP08	154.80	244.6	185.7	209.4	-	155.8	244	185.9	209.1	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K8-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550K8-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550K8-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K8-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K8-625AXSP08	162.20	254.1	193.9	218.1	-	163.5	253.5	194.3	217.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K8-632AXSP08	154.80	244.6	185.7	209.4	-	155.8	244	185.9	209.1	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K9-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550K9-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550K9-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K9-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550K9-625AXSP08	162.20	254.1	193.9	218.1	-	163.5	253.5	194.3	217.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550K9-632AXSP08	154.80	244.6	185.7	209.4	-	155.8	244	185.9	209.1	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB550R3-425AXSP06	131.20	215.2	160.9	183	-	133.6	216	162.2	184	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB550R3-432AXSP08	128.50	207.3	155.8	176.7	-	129.5	206.9	156.1	176.6	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB550R3-525AXSP08	151.30	239.4	181.8	205.2	-	152.5	239.3	182.1	205.1	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550R3-532AXSP08	142.00	226.9	171.3	194	-	143.3	226.3	171.8	193.6	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB550R3-625AXSP08	162.20	254.1	193.9	218.1	-	163.5													

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZB750K9-625AXSP08	170.30	267.1	203.7	229.3	-	172	266.9	204.3	229.4	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB750K9-632AXSP08	162.50	257.2	195.2	220.3	-	164.1	257.2	195.9	220.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB750R3-425AXSP06	135.90	222.9	166.5	189.6	-	138.2	223.6	167.9	190.6	-	203	18.1	3"	162	11.9	3"	244	25.5	3"
EAW-FD1553ZB750R3-432AXSP08	133.00	214.7	161.4	183	-	134.1	214.6	161.8	183.1	-	152	21.7	3"	122	14.3	3"	183	30.4	3"
EAW-FD1553ZB750R3-525AXSP08	156.00	247.3	187.5	211.8	-	157.3	247.3	188.2	211.7	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB750R3-532AXSP08	146.70	234.7	177.2	200.4	-	148	234.3	177.6	200.3	-	186	22.6	3"	149	14.9	3"	223	31.7	3"
EAW-FD1553ZB750R3-625AXSP08	166.80	261.7	199.4	224.5	-	168.3	261.4	199.9	224.5	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZB750R3-632AXSP08	159.30	252.1	191.5	215.7	-	160.7	252	191.8	215.8	-	225	23.8	3"	180	15.7	3"	270	29.7	4"
EAW-FD1553ZK370C2-425AXSP06	135.60	219.5	165.1	187	-	137.2	219.6	165.6	187.5	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370C2-432AXSP08	132.00	210.9	159.3	180.2	-	132.7	210	159.2	179.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370C2-525AXSP08	154.70	243	185.1	208.2	-	155.6	242.1	184.8	207.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C2-532AXSP08	146.10	230.8	175.3	197.6	-	146.6	230.1	175.1	197.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C2-625AXSP08	165.50	256.1	196.5	220.4	-	166.2	255.3	196.5	219.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C2-632AXSP08	158.50	248	189.5	212.9	-	159.3	247	189	212.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C4-425AXSP06	135.60	219.5	165.1	187	-	137.2	219.6	165.6	187.5	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370C4-432AXSP08	132.00	210.9	159.3	180.2	-	132.7	210	159.2	179.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370C4-525AXSP08	154.70	243	185.1	208.2	-	155.6	242.1	184.8	207.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C4-532AXSP08	146.10	230.8	175.3	197.6	-	146.6	230.1	175.1	197.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C4-625AXSP08	165.50	256.1	196.5	220.4	-	166.2	255.3	196.5	219.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C4-632AXSP08	158.50	248	189.5	212.9	-	159.3	247	189	212.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C5-425AXSP06	135.60	219.5	165.1	187	-	137.2	219.6	165.6	187.5	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370C5-432AXSP08	132.00	210.9	159.3	180.2	-	132.7	210	159.2	179.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370C5-525AXSP08	154.70	243	185.1	208.2	-	155.6	242.1	184.8	207.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C5-532AXSP08	146.10	230.8	175.3	197.6	-	146.6	230.1	175.1	197.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C5-625AXSP08	165.50	256.1	196.5	220.4	-	166.2	255.3	196.5	219.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C5-632AXSP08	158.50	248	189.5	212.9	-	159.3	247	189	212.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C8-425AXSP06	135.60	219.5	165.1	187	-	137.2	219.6	165.6	187.5	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370C8-432AXSP08	132.00	210.9	159.3	180.2	-	132.7	210	159.2	179.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370C8-525AXSP08	154.70	243	185.1	208.2	-	155.6	242.1	184.8	207.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C8-532AXSP08	146.10	230.8	175.3	197.6	-	146.6	230.1	175.1	197.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370C8-625AXSP08	165.50	256.1	196.5	220.4	-	166.2	255.3	196.5	219.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370C8-632AXSP08	158.50	248	189.5	212.9	-	159.3	247	189	212.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K2-425AXSP06	131.20	212.4	159.7	181.2	-	132.7	212.3	160.1	181.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370K2-432AXSP08	127.80	203.9	154.1	174.3	-	128.3	203.2	153.8	173.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370K2-525AXSP08	150.50	235.6	179.7	202.3	-	151.1	234.4	179.4	201.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K2-532AXSP08	141.40	223.8	169.9	191.4	-	142.1	222.7	169.7	190.7	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K2-625AXSP08	161.70	250	191.9	215.2	-	162.2	248.6	191.4	214.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K2-632AXSP08	154.10	241	184.1	206.7	-	154.8	239.7	183.6	205.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K4-425AXSP06	131.20	212.4	159.7	181.2	-	132.7	212.3	160.1	181.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370K4-432AXSP08	127.80	203.9	154.1	174.3	-	128.3	203.2	153.8	173.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370K4-525AXSP08	150.50	235.6	179.7	202.3	-	151.1	234.4	179.4	201.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K4-532AXSP08	141.40	223.8	169.9	191.4	-	142.1	222.7	169.7	190.7	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K4-625AXSP08	161.70	250	191.9	215.2	-	162.2	248.6	191.4	214.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K4-632AXSP08	154.10	241	184.1	206.7	-	154.8	239.7	183.6	205.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K5-425AXSP06	131.20	212.4	159.7	181.2	-	132.7	212.3	160.1	181.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370K5-432AXSP08	127.80	203.9	154.1	174.3	-	128.3	203.2	153.8	173.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370K5-525AXSP08	150.50	235.6	179.7	202.3	-	151.1	234.4	179.4	201.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K5-532AXSP08	141.40	223.8	169.9	191.4	-	142.1	222.7	169.7	190.7	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K5-625AXSP08	161.70	250	191.9	215.2	-	162.2	248.6	191.4	214.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K5-632AXSP08	154.10	241	184.1	206.7	-	154.8	239.7	183.6	205.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K8-425AXSP06	131.20	212.4	159.7	181.2	-	132.7	212.3	160.1	181.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK370K8-432AXSP08	127.80	203.9	154.1	174.3	-	128.3	203.2	153.8	173.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK370K8-525AXSP08	150.50	235.6	179.7	202.3	-	151.1	234.4	179.4	201.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K8-532AXSP08	141.40	223.8	169.9	191.4	-	142.1	222.7	169.7	190.7	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK370K8-625AXSP08	161.70	250	191.9	215.2	-	162.2	248.6	191.4	214.2	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK370K8-632AXSP08	154.10	241	184.1	206.7	-	154.8	239.7	183.6	205.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK400B3-425AXSP06	131.10	212.2	159.5	181	-	132.8	212.1	160.2	181.2	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK400B3-432AXSP08	128.30	204.6	154.7	175	-	128.8	204.2	154.5	174.5	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK400B3-525AXSP08	149.20	233.5	178.2	200.6	-	149.9	232.9	178.3	200	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK400B3-532AXSP08	141.10	222.9	169.5	191	-	141.9	222.2	169.3	190.6	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK400B3-625AXSP08	158.70	245.3	188.4	211.2	-	159.6	244.7	188.5	210.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK400B3-632AXSP08	152.90	238.7	182.4	204.8	-	153.7	237.9	182.4	204.3	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK400C3-425AXSP06	135.60	219.5	165.1	187	-	137.2	219.6	165.6	187.5	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK400C3-432AXSP08	132.00	210.9	159.3	180.2	-	132.7	210	159.2	179.6	-	152	23.7	3"	122	15.6	3"	183	33.2	3"
EAW-FD1553ZK400C3-525AXSP08	154.70	243	185.1	208.2	-	155.6	242.1	184.8	207.8	-	186	24							

EAW-FD1553ZK550C2-532AXSP08	161.50	256.5	194.1	219.3	-	162.6	255.6	194.2	218.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550C2-625AXSP08	184.90	287.5	219.8	246.9	-	185.7	286.6	220.1	246.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C2-632AXSP08	176.00	276.5	210.7	237.1	-	177.2	275.8	210.6	236.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C3-425AXSP06	150.30	244	183	208	-	152.2	244.2	183.9	208.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C3-432AXSP06	138.80	226.8	169.7	193	-	140.5	227	170.4	193.3	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C3-525AXSP06	166.60	267.4	201.8	228.3	-	168.6	267.4	202.6	228.6	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK550C3-532AXSP08	161.50	256.5	194.1	219.3	-	162.6	255.6	194.2	218.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550C3-625AXSP08	184.90	287.5	219.8	246.9	-	185.7	286.6	220.1	246.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C3-632AXSP08	176.00	276.5	210.7	237.1	-	177.2	275.8	210.6	236.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C4-425AXSP06	150.30	244	183	208	-	152.2	244.2	183.9	208.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C4-432AXSP06	138.80	226.8	169.7	193	-	140.5	227	170.4	193.3	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C4-525AXSP06	166.60	267.4	201.8	228.3	-	168.6	267.4	202.6	228.6	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK550C4-532AXSP08	161.50	256.5	194.1	219.3	-	162.6	255.6	194.2	218.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550C4-625AXSP08	184.90	287.5	219.8	246.9	-	185.7	286.6	220.1	246.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C4-632AXSP08	176.00	276.5	210.7	237.1	-	177.2	275.8	210.6	236.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C8-425AXSP06	150.30	244	183	208	-	152.2	244.2	183.9	208.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C8-432AXSP06	138.80	226.8	169.7	193	-	140.5	227	170.4	193.3	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C8-525AXSP06	166.60	267.4	201.8	228.3	-	168.6	267.4	202.6	228.6	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK550C8-532AXSP08	161.50	256.5	194.1	219.3	-	162.6	255.6	194.2	218.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550C8-625AXSP08	184.90	287.5	219.8	246.9	-	185.7	286.6	220.1	246.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C8-632AXSP08	176.00	276.5	210.7	237.1	-	177.2	275.8	210.6	236.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C9-425AXSP06	150.30	244	183	208	-	152.2	244.2	183.9	208.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C9-432AXSP06	138.80	226.8	169.7	193	-	140.5	227	170.4	193.3	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550C9-525AXSP06	166.60	267.4	201.8	228.3	-	168.6	267.4	202.6	228.6	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK550C9-532AXSP08	161.50	256.5	194.1	219.3	-	162.6	255.6	194.2	218.8	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550C9-625AXSP08	184.90	287.5	219.8	246.9	-	185.7	286.6	220.1	246.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550C9-632AXSP08	176.00	276.5	210.7	237.1	-	177.2	275.8	210.6	236.8	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K2-425AXSP06	143.80	233.2	175	198.7	-	145.5	233.2	175.9	199	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K2-432AXSP06	133.10	217.2	162.5	184.8	-	134.7	217.4	163.2	185.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K2-525AXSP08	164.60	259	197.2	222	-	165.6	258.2	197.2	221.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K2-532AXSP08	154.80	245.2	186	209.9	-	155.5	244.6	185.9	209.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K2-625AXSP08	177.20	275.1	210.9	236.7	-	177.9	274	210.7	236	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K2-632AXSP08	168.80	264.5	201.6	226.7	-	169.4	263.5	201.5	226.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K3-425AXSP06	143.80	233.2	175	198.7	-	145.5	233.2	175.9	199	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K3-432AXSP06	133.10	217.2	162.5	184.8	-	134.7	217.4	163.2	185.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K3-525AXSP08	164.60	259	197.2	222	-	165.6	258.2	197.2	221.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K3-532AXSP08	154.80	245.2	186	209.9	-	155.5	244.6	185.9	209.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K3-625AXSP08	177.20	275.1	210.9	236.7	-	177.9	274	210.7	236	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K3-632AXSP08	168.80	264.5	201.6	226.7	-	169.4	263.5	201.5	226.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K4-425AXSP06	143.80	233.2	175	198.7	-	145.5	233.2	175.9	199	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K4-432AXSP06	133.10	217.2	162.5	184.8	-	134.7	217.4	163.2	185.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K4-525AXSP08	164.60	259	197.2	222	-	165.6	258.2	197.2	221.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K4-532AXSP08	154.80	245.2	186	209.9	-	155.5	244.6	185.9	209.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K4-625AXSP08	177.20	275.1	210.9	236.7	-	177.9	274	210.7	236	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K4-632AXSP08	168.80	264.5	201.6	226.7	-	169.4	263.5	201.5	226.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K5-425AXSP06	143.80	233.2	175	198.7	-	145.5	233.2	175.9	199	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K5-432AXSP06	133.10	217.2	162.5	184.8	-	134.7	217.4	163.2	185.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K5-525AXSP08	164.60	259	197.2	222	-	165.6	258.2	197.2	221.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K5-532AXSP08	154.80	245.2	186	209.9	-	155.5	244.6	185.9	209.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K5-625AXSP08	177.20	275.1	210.9	236.7	-	177.9	274	210.7	236	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K5-632AXSP08	168.80	264.5	201.6	226.7	-	169.4	263.5	201.5	226.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K8-425AXSP06	143.80	233.2	175	198.7	-	145.5	233.2	175.9	199	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K8-432AXSP06	133.10	217.2	162.5	184.8	-	134.7	217.4	163.2	185.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K8-525AXSP08	164.60	259	197.2	222	-	165.6	258.2	197.2	221.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K8-532AXSP08	154.80	245.2	186	209.9	-	155.5	244.6	185.9	209.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K8-625AXSP08	177.20	275.1	210.9	236.7	-	177.9	274	210.7	236	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K8-632AXSP08	168.80	264.5	201.6	226.7	-	169.4	263.5	201.5	226.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K9-425AXSP06	143.80	233.2	175	198.7	-	145.5	233.2	175.9	199	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K9-432AXSP06	133.10	217.2	162.5	184.8	-	134.7	217.4	163.2	185.1	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550K9-525AXSP08	164.60	259	197.2	222	-	165.6	258.2	197.2	221.5	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K9-532AXSP08	154.80	245.2	186	209.9	-	155.5	244.6	185.9	209.2	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK550K9-625AXSP08	177.20	275.1	210.9	236.7	-	177.9	274	210.7	236	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550K9-632AXSP08	168.80	264.5	201.6	226.7	-	169.4	263.5	201.5	226.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK550R3-425AXSP06	146.70	238.1	178.5	202.8	-	148.5	238.4	179.6	203.3	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550R3-432AXSP06	135.70	221.7	165.8	188.7	-	137.3	221.8	166.6	188.9	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK550R3-525AXSP08	167.90	264.5	201.2	226.6	-	169	263.3	201	226.2	-	186	24.6							

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZK750K4-625AXSP08	187.10	291.3	222.6	250	-	188.1	290.4	222.9	249.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K4-632AXSP08	178.00	279.9	213.2	240	-	179.3	279.3	213.1	239.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K5-425AXSP06	152.30	247.2	185.5	210.6	-	154.2	247.8	186.6	211.4	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750K5-432AXSP06	141.00	230.6	172.4	196.2	-	142.8	230.8	173.2	196.4	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750K5-525AXSP06	168.60	270.4	204.2	231.2	-	170.7	270.8	205.1	231.5	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK750K5-532AXSP08	163.60	259.6	196.6	222.2	-	164.5	259.3	196.9	221.9	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK750K5-625AXSP08	187.10	291.3	222.6	250	-	188.1	290.4	222.9	249.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K5-632AXSP08	178.00	279.9	213.2	240	-	179.3	279.3	213.1	239.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K8-425AXSP06	152.30	247.2	185.5	210.6	-	154.2	247.8	186.6	211.4	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750K8-432AXSP06	141.00	230.6	172.4	196.2	-	142.8	230.8	173.2	196.4	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750K8-525AXSP06	168.60	270.4	204.2	231.2	-	170.7	270.8	205.1	231.5	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK750K8-532AXSP08	163.60	259.6	196.6	222.2	-	164.5	259.3	196.9	221.9	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK750K8-625AXSP08	187.10	291.3	222.6	250	-	188.1	290.4	222.9	249.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K8-632AXSP08	178.00	279.9	213.2	240	-	179.3	279.3	213.1	239.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K9-425AXSP06	152.30	247.2	185.5	210.6	-	154.2	247.8	186.6	211.4	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750K9-432AXSP06	141.00	230.6	172.4	196.2	-	142.8	230.8	173.2	196.4	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750K9-525AXSP06	168.60	270.4	204.2	231.2	-	170.7	270.8	205.1	231.5	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK750K9-532AXSP08	163.60	259.6	196.6	222.2	-	164.5	259.3	196.9	221.9	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK750K9-625AXSP08	187.10	291.3	222.6	250	-	188.1	290.4	222.9	249.9	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750K9-632AXSP08	178.00	279.9	213.2	240	-	179.3	279.3	213.1	239.7	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750R3-425AXSP06	149.2	242.3	181.8	206.6	-	151.2	242.7	182.8	206.9	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750R3-432AXSP06	138.2	226.1	169.1	192.2	-	140.1	226.3	169.9	192.7	-	203	19.6	3"	162	12.9	3"	244	27.5	3"
EAW-FD1553ZK750R3-525AXSP06	165	264.7	199.8	226.1	-	167	265.1	200.9	226.7	-	254	21.4	3"	203	14.1	3"	304	25.3	4"
EAW-FD1553ZK750R3-532AXSP08	160.2	254.4	192.9	217.5	-	161.1	253.6	192.7	217.1	-	186	24.6	3"	149	16.2	3"	223	34.5	3"
EAW-FD1553ZK750R3-625AXSP08	183	284.6	217.9	244.7	-	184.1	284	217.8	244.1	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1553ZK750R3-632AXSP08	174.6	274.2	208.7	235.2	-	175.4	273	208.9	234.5	-	225	25.8	3"	180	17	3"	270	32.4	4"
EAW-FD1554PB370C2-425AXSP04	144.8	243.9	181.2	206.7	423.6	148.8	245.4	183.4	208.5	422.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB370C2-432AXSP06	148.9	240.4	180.7	204.7	-	150.3	239.9	181.1	205	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370C2-525AXSP06	174.7	276.3	209.7	236.5	-	176.6	276.3	210.7	237	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C2-532AXSP06	165.8	264.1	199.9	226.1	-	167.3	264.3	200.5	226.1	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C2-625AXSP06	184	287.3	219.4	246.6	-	185.7	287.3	220.3	247.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C2-632AXSP06	177.2	279.8	212.8	239.8	-	179.3	279.9	213.7	240.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C4-425AXSP04	144.8	243.9	181.2	206.7	423.6	148.8	245.4	183.4	208.5	422.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB370C4-432AXSP06	148.9	240.4	180.7	204.7	-	150.3	239.9	181.1	205	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370C4-525AXSP06	174.7	276.3	209.7	236.5	-	176.6	276.3	210.7	237	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C4-532AXSP06	165.8	264.1	199.9	226.1	-	167.3	264.3	200.5	226.1	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C4-625AXSP06	184	287.3	219.4	246.6	-	185.7	287.3	220.3	247.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C4-632AXSP06	177.2	279.8	212.8	239.8	-	179.3	279.9	213.7	240.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C5-425AXSP04	144.8	243.9	181.2	206.7	423.6	148.8	245.4	183.4	208.5	422.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB370C5-432AXSP06	148.9	240.4	180.7	204.7	-	150.3	239.9	181.1	205	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370C5-525AXSP06	174.7	276.3	209.7	236.5	-	176.6	276.3	210.7	237	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C5-532AXSP06	165.8	264.1	199.9	226.1	-	167.3	264.3	200.5	226.1	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C5-625AXSP06	184	287.3	219.4	246.6	-	185.7	287.3	220.3	247.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C5-632AXSP06	177.2	279.8	212.8	239.8	-	179.3	279.9	213.7	240.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C8-425AXSP04	144.8	243.9	181.2	206.7	423.6	148.8	245.4	183.4	208.5	422.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB370C8-432AXSP06	148.9	240.4	180.7	204.7	-	150.3	239.9	181.1	205	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370C8-525AXSP06	174.7	276.3	209.7	236.5	-	176.6	276.3	210.7	237	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C8-532AXSP06	165.8	264.1	199.9	226.1	-	167.3	264.3	200.5	226.1	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370C8-625AXSP06	184	287.3	219.4	246.6	-	185.7	287.3	220.3	247.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370C8-632AXSP06	177.2	279.8	212.8	239.8	-	179.3	279.9	213.7	240.2	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370K2-425AXSP06	156.4	250.4	188.9	213.7	-	157.6	249.7	189.2	213.8	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370K2-432AXSP06	145.3	234.1	176.1	199.6	-	146.3	233.7	176.4	199.5	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370K2-525AXSP06	172.5	272.5	206.9	233.3	-	173.7	272	207.6	233.5	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370K2-532AXSP06	162.6	259.2	196	221.6	-	163.7	258.7	196.4	221.5	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370K2-625AXSP06	183.4	286.4	219	246.1	-	184.9	285.9	219.3	245.7	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370K2-632AXSP06	175.3	276.5	210.4	237	-	176.7	276.2	210.6	237	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370K4-425AXSP06	156.4	250.4	188.9	213.7	-	157.6	249.7	189.2	213.8	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370K4-432AXSP06	145.3	234.1	176.1	199.6	-	146.3	233.7	176.4	199.5	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370K4-525AXSP06	172.5	272.5	206.9	233.3	-	173.7	272	207.6	233.5	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370K4-532AXSP06	162.6	259.2	196	221.6	-	163.7	258.7	196.4	221.5	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB370K4-625AXSP06	183.4	286.4	219	246.1	-	184.9	285.9	219.3	245.7	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370K4-632AXSP06	175.3	276.5	210.4	237	-	176.7	276.2	210.6	237	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB370K5-425AXSP06	156.4	250.4	188.9	213.7	-	157.6	249.7	189.2	213.8	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370K5-432AXSP06	145.3	234.1	176.1	199.6	-	146.3	233.7	176.4	199.5	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB370K5-525AXSP06	172.5	272.5	206.9	233.3	-	173.7	272	207.6	233.5	-	225	23.2	3"	1					

EAW-FD1554PB400K9-532AXSP06	162.6	259.2	196	221.6	-	163.7	258.7	196.4	221.5	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB400K9-625AXSP06	183.4	286.4	219	246.1	-	184.9	285.9	219.3	245.7	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB400K9-632AXSP06	175.3	276.5	210.4	237	-	176.7	276.2	210.6	237	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB400R3-425AXSP06	158	253.1	190.8	215.9	-	159.2	252.5	191.1	216	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB400R3-432AXSP06	146.9	236.6	177.9	201.7	-	148	236.3	178.3	201.7	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB400R3-525AXSP06	174.2	275.3	209	235.7	-	175.5	274.9	209.4	235.5	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB400R3-532AXSP06	164.1	261.8	197.9	223.7	-	165.6	261.4	198.4	223.7	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB400R3-625AXSP06	185	289	220.9	248.4	-	186.6	288.7	221.4	248	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB400R3-632AXSP06	176.9	279.2	212.5	239.3	-	178.5	278.6	212.7	239.1	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550B3-425AXSP04	149.7	251.4	186.8	213.5	437.6	153.9	253.6	189.5	215.7	437.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550B3-432AXSP06	154	248.7	186.8	212.1	-	155.7	248.7	187.8	212.5	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB550B3-525AXSP04	-	-	-	-	-	-	-	-	-	-	338	15.7	4"	270	10.3	4"	406	22.1	4"
EAW-FD1554PB550B3-532AXSP06	-	-	-	-	-	172.4	272.4	206.7	233.2	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.1	4"	487	19.5	(2) 4"
EAW-FD1554PB550B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.1	4"	487	19.5	(2) 4"
EAW-FD1554PB550C2-425AXSP04	160.9	269.7	200.1	228.7	-	165	271.5	202.7	230.8	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C2-432AXSP04	148.2	251.4	186.1	213.1	441.1	152.2	253.2	188.4	214.8	440.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C2-525AXSP06	193.4	307	233	262.8	-	195.5	307.7	234	263.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C2-532AXSP06	182.6	292.2	220.5	249.8	-	184.5	292.4	221.5	250.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C2-632AXSP06	-	-	-	-	-	198.1	311.2	237	266.4	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550C3-425AXSP04	160.9	269.7	200.1	228.7	-	165	271.5	202.7	230.8	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C3-432AXSP04	148.2	251.4	186.1	213.1	441.1	152.2	253.2	188.4	214.8	440.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C3-525AXSP06	193.4	307	233	262.8	-	195.5	307.7	234	263.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C3-532AXSP06	182.6	292.2	220.5	249.8	-	184.5	292.4	221.5	250.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.1	4"	487	19.5	(2) 4"
EAW-FD1554PB550C3-632AXSP06	-	-	-	-	-	198.1	311.2	237	266.4	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550C4-425AXSP04	160.9	269.7	200.1	228.7	-	165	271.5	202.7	230.8	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C4-432AXSP04	148.2	251.4	186.1	213.1	441.1	152.2	253.2	188.4	214.8	440.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C4-525AXSP06	193.4	307	233	262.8	-	195.5	307.7	234	263.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C4-532AXSP06	182.6	292.2	220.5	249.8	-	184.5	292.4	221.5	250.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C4-632AXSP06	-	-	-	-	-	198.1	311.2	237	266.4	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550C5-425AXSP04	160.9	269.7	200.1	228.7	-	165	271.5	202.7	230.8	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C5-432AXSP04	148.2	251.4	186.1	213.1	441.1	152.2	253.2	188.4	214.8	440.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C5-525AXSP06	193.4	307	233	262.8	-	195.5	307.7	234	263.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C5-532AXSP06	182.6	292.2	220.5	249.8	-	184.5	292.4	221.5	250.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C5-632AXSP06	-	-	-	-	-	198.1	311.2	237	266.4	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550C8-425AXSP04	160.9	269.7	200.1	228.7	-	165	271.5	202.7	230.8	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C8-432AXSP04	148.2	251.4	186.1	213.1	441.1	152.2	253.2	188.4	214.8	440.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C8-525AXSP06	193.4	307	233	262.8	-	195.5	307.7	234	263.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C8-532AXSP06	182.6	292.2	220.5	249.8	-	184.5	292.4	221.5	250.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C8-632AXSP06	-	-	-	-	-	198.1	311.2	237	266.4	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550C9-425AXSP04	160.9	269.7	200.1	228.7	-	165	271.5	202.7	230.8	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C9-432AXSP04	148.2	251.4	186.1	213.1	441.1	152.2	253.2	188.4	214.8	440.2	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550C9-525AXSP06	193.4	307	233	262.8	-	195.5	307.7	234	263.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C9-532AXSP06	182.6	292.2	220.5	249.8	-	184.5	292.4	221.5	250.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550C9-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.1	4"	487	19.5	(2) 4"
EAW-FD1554PB550C9-632AXSP06	-	-	-	-	-	198.1	311.2	237	266.4	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K2-425AXSP04	154.6	259.3	192.7	219.9	451.4	158.5	260.8	194.9	221.6	450.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550K2-432AXSP06	157.5	254.2	190.9	216.6	-	158.8	254	191.7	216.7	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB550K2-525AXSP06	187.2	296.9	225	254.1	-	189	296.9	225.8	254.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550K2-532AXSP06	176.2	281.8	213	240.7	-	177.9	281.7	213.4	241	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550K2-625AXSP06	199.3	312	238.2	267.7	-	201	312.1	238.7	268	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K2-632AXSP06	190.1	300.9	228.2	257.4	-	191.8	300.6	228.9	257.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K3-425AXSP04	154.6	259.3	192.7	219.9	451.4	158.5	260.8	194.9	221.6	450.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550K3-432AXSP06	157.5	254.2	190.9	216.6	-	158.8	254	191.7	216.7	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB550K3-525AXSP06	187.2	296.9	225	254.1	-	189	296.9	225.8	254.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550K3-532AXSP06	176.2	281.8	213	240.7	-	177.9	281.7	213.4	241	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550K3-625AXSP06	199.3	312	238.2	267.7	-	201	312.1	238.7	268	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K3-632AXSP06	190.1	300.9	228.2	257.4	-	191.8	300.6	228.9	257.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K4-425AXSP04	154.6	259.3	192.7	219.9	451.4	158.5	260.8	194.9	221.6	450.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550K4-432AXSP06	157.5	254.2	190.9	216.6	-	158.8	254	191.7	216.7	-	180	21.8	3"	144	14.4	3"	216	30.7	3"
EAW-FD1554PB550K4-525AXSP06	187.2	296.9	225	254.1	-	189	296.9	225.8	254.3	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550K4-532AXSP06	176.2	281.8	213	240.7	-	177.9	281.7	213.4	241	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB550K4-625AXSP06	199.3	312	238.2	267.7	-	201	312.1	238.7	268	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K4-632AXSP06	190.1	300.9	228.2	257.4	-	191.8	300.6	228.9	257.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB550K5-425AXSP04	154.6	259.3	192.7	219.9	451.4	158.5	260.8	194.9	221.6	450.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB550K5-432AXSP06	157.5	254.2	190.9	216.6	-	158.8	254	191.7	216.7	-									

EAW-FD1554PB750K4-425AXSP04	162.7	272.7	202.2	231.2	-	167	274.6	204.9	233.4	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K4-432AXSP04	149.9	254	188.1	215.1	446	154	255.9	190.4	217	444.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K4-525AXSP06	195.9	311.2	235.7	266.3	-	197.8	311.7	237	266.6	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K4-532AXSP06	184.6	295.5	223.2	252.5	-	186.5	295.7	223.8	253	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K4-625AXSP06	208.2	326.7	249	280	-	210.1	326.9	250	280.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K4-632AXSP06	198.9	314.6	238.9	269.7	-	200.6	314.9	239.6	269.8	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K5-425AXSP04	162.7	272.7	202.2	231.2	-	167	274.6	204.9	233.4	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K5-432AXSP04	149.9	254	188.1	215.1	446	154	255.9	190.4	217	444.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K5-525AXSP06	195.9	311.2	235.7	266.3	-	197.8	311.7	237	266.6	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K5-532AXSP06	184.6	295.5	223.2	252.5	-	186.5	295.7	223.8	253	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K5-625AXSP06	208.2	326.7	249	280	-	210.1	326.9	250	280.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K5-632AXSP06	198.9	314.6	238.9	269.7	-	200.6	314.9	239.6	269.8	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K8-425AXSP04	162.7	272.7	202.2	231.2	-	167	274.6	204.9	233.4	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K8-432AXSP04	149.9	254	188.1	215.1	446	154	255.9	190.4	217	444.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K8-525AXSP06	195.9	311.2	235.7	266.3	-	197.8	311.7	237	266.6	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K8-532AXSP06	184.6	295.5	223.2	252.5	-	186.5	295.7	223.8	253	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K8-625AXSP06	208.2	326.7	249	280	-	210.1	326.9	250	280.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K8-632AXSP06	198.9	314.6	238.9	269.7	-	200.6	314.9	239.6	269.8	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K9-425AXSP04	162.7	272.7	202.2	231.2	-	167	274.6	204.9	233.4	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K9-432AXSP04	149.9	254	188.1	215.1	446	154	255.9	190.4	217	444.3	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750K9-525AXSP06	195.9	311.2	235.7	266.3	-	197.8	311.7	237	266.6	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K9-532AXSP06	184.6	295.5	223.2	252.5	-	186.5	295.7	223.8	253	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750K9-625AXSP06	208.2	326.7	249	280	-	210.1	326.9	250	280.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750K9-632AXSP06	198.9	314.6	238.9	269.7	-	200.6	314.9	239.6	269.8	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750R3-425AXSP04	159.3	267.2	198.4	226.6	-	163.6	269.4	209.9	228.7	-	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750R3-432AXSP04	146.9	249.5	184.6	211.3	437	151	251	186.8	213	436.1	270	14.7	4"	216	12.1	3"	325	20.6	4"
EAW-FD1554PB750R3-525AXSP06	192.1	304.8	231	261	-	193.9	305.2	232.2	261.6	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750R3-532AXSP06	181.1	289.6	219	247.6	-	182.9	290.2	219.5	248	-	225	23.2	3"	180	15.3	3"	270	28.9	4"
EAW-FD1554PB750R3-625AXSP06	204.2	320	244.1	274.4	-	206	320.2	245	274.8	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554PB750R3-632AXSP06	194.8	308.8	234.4	264.5	-	196.8	308.5	235.4	264.5	-	270	21.2	4"	216	16.4	3"	325	29.7	4"
EAW-FD1554ZB730C2-425AXSP06	173.7	278	209.9	237.3	-	175.1	277.8	210.2	237.4	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C2-432AXSP06	161.6	260.4	195.8	222.1	-	162.8	259.8	196.2	221.8	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C2-525AXSP06	190.9	301.4	229	258.1	-	192.5	301	229.5	258.5	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C2-532AXSP06	180.6	287.6	217.7	246	-	182.2	287.1	218.1	245.9	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C2-625AXSP06	202.1	315.3	240.9	270.7	-	203.9	315	241.8	270.7	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C2-632AXSP06	194	306.2	232.9	262.2	-	195.7	305.6	233.2	262.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C4-425AXSP06	173.7	278	209.9	237.3	-	175.1	277.8	210.2	237.4	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C4-432AXSP06	161.6	260.4	195.8	222.1	-	162.8	259.8	196.2	221.8	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C4-525AXSP06	190.9	301.4	229	258.1	-	192.5	301	229.5	258.5	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C4-532AXSP06	180.6	287.6	217.7	246	-	182.2	287.1	218.1	245.9	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C4-625AXSP06	202.1	315.3	240.9	270.7	-	203.9	315	241.8	270.7	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C4-632AXSP06	194	306.2	232.9	262.2	-	195.7	305.6	233.2	262.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C5-425AXSP06	173.7	278	209.9	237.3	-	175.1	277.8	210.2	237.4	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C5-432AXSP06	161.6	260.4	195.8	222.1	-	162.8	259.8	196.2	221.8	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C5-525AXSP06	190.9	301.4	229	258.1	-	192.5	301	229.5	258.5	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C5-532AXSP06	180.6	287.6	217.7	246	-	182.2	287.1	218.1	245.9	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C5-625AXSP06	202.1	315.3	240.9	270.7	-	203.9	315	241.8	270.7	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C5-632AXSP06	194	306.2	232.9	262.2	-	195.7	305.6	233.2	262.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C8-425AXSP06	173.7	278	209.9	237.3	-	175.1	277.8	210.2	237.4	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C8-432AXSP06	161.6	260.4	195.8	222.1	-	162.8	259.8	196.2	221.8	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730C8-525AXSP06	190.9	301.4	229	258.1	-	192.5	301	229.5	258.5	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C8-532AXSP06	180.6	287.6	217.7	246	-	182.2	287.1	218.1	245.9	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730C8-625AXSP06	202.1	315.3	240.9	270.7	-	203.9	315	241.8	270.7	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730C8-632AXSP06	194	306.2	232.9	262.2	-	195.7	305.6	233.2	262.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730K2-425AXSP06	169	270.1	203.8	230.8	-	170.2	269.4	204.2	230.5	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730K2-432AXSP06	156.8	252.3	190.1	215.2	-	158	251.9	190.2	214.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730K2-525AXSP06	186.8	294.5	223.9	252.3	-	188.1	293.8	224.2	252	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730K2-532AXSP06	175.9	280.1	211.9	239.3	-	177.1	279.1	212	238.8	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730K2-625AXSP06	199.1	310.3	237.2	266.5	-	200.5	309.5	237.7	266.1	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730K2-632AXSP06	189.8	299.2	227.7	256.8	501.3	191	298.3	227.9	255.9	496.3	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730K4-425AXSP06	169	270.1	203.8	230.8	-	170.2	269.4	204.2	230.5	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730K4-432AXSP06	156.8	252.3	190.1	215.2	-	158	251.9	190.2	214.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB730K4-525AXSP06	186.8	294.5	223.9	252.3	-	188.1	293.8	224.2	252	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730K4-532AXSP06	175.9	280.1	211.9	239.3	-	177.1	279.1	212	238.8	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB730K4-625AXSP06	199.1	310.3	237.2	266.5	-	200.5	309.5	237.7	266.1	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB730K4-632AXSP06	189.8	299.																	

EAW-FD1554ZB400K3-632AXSP06	189.8	299.2	227.7	256.8	501.3	191	298.3	227.9	255.9	496.3	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB400K9-425AXSP06	169	270.1	203.8	230.8	-	170.2	269.4	204.2	230.5	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB400K9-432AXSP06	156.8	252.3	190.1	215.2	-	158	251.9	190.2	214.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB400K9-525AXSP06	186.8	294.5	223.9	252.3	-	188.1	293.8	224.2	252	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB400K9-532AXSP06	175.9	280.1	211.9	239.3	-	177.1	279.1	212	238.8	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB400K9-625AXSP06	199.1	310.3	237.2	266.5	-	200.5	309.5	237.7	266.1	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB400K9-632AXSP06	189.8	299.2	227.7	256.8	501.3	191	298.3	227.9	255.9	496.3	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB400R3-423AXSP06	171	273.4	206.2	233.6	-	172.3	272.9	206.7	233.4	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB400R3-432AXSP06	158.7	255.6	192.2	217.9	-	160	254.9	192.5	217.6	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB400R3-525AXSP06	188.7	297.8	226.3	255.1	-	190.2	297.2	226.7	254.9	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB400R3-532AXSP06	177.8	282.9	214.2	242	-	179.2	282.5	214.5	241.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB400R3-625AXSP06	201.2	313.7	239.7	269.4	-	202.6	312.6	239.9	269	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB400R3-632AXSP06	191.7	302.5	230.5	259.5	506.9	193.3	301.7	230.3	259.1	502.1	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550R3-425AXSP04	163.6	275.4	204.6	233.7	478.5	168	277.1	207.2	235.4	476.9	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550R3-432AXSP06	168.2	271.5	204	231.2	-	169.7	270.9	204.5	231.5	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550R3-525AXSP06	197.2	312	236.7	267	-	199.3	311.8	237.8	267.5	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550R3-532AXSP06	187.1	298.1	225.6	255.2	-	188.9	298.5	226.4	255.4	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550R3-625AXSP04	-	-	-	-	-	-	-	-	-	-	456	14.2	(2) 4"	365	11.9	4"	548	19.9	(2) 4"
EAW-FD1554ZB550R3-632AXSP06	-	-	-	-	-	202.3	316	241.2	271.1	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C2-432AXSP04	174.9	293.2	218	248.9	-	179.3	294.9	220.5	250.8	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550C2-432AXSP06	177.8	287.2	215.8	244.9	-	179.4	287.1	216.3	244.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550C2-525AXSP06	211.9	336.2	255.1	287.6	-	214	336.3	255.7	288	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C2-532AXSP06	199.4	318.7	240.8	272.7	-	201.1	318.7	241.3	272.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C2-625AXSP06	225.2	352.7	269.2	302.5	-	227.2	352.8	270.1	302.9	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C2-632AXSP06	215.1	340.5	258.6	291.7	-	217	340.4	259.5	292	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C3-425AXSP04	174.9	293.2	218	248.9	-	179.3	294.9	220.5	250.8	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550C3-432AXSP06	177.8	287.2	215.8	244.9	-	179.4	287.1	216.3	244.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550C3-525AXSP06	211.9	336.2	255.1	287.6	-	214	336.3	255.7	288	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C3-532AXSP06	199.4	318.7	240.8	272.7	-	201.1	318.7	241.3	272.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C3-625AXSP06	225.2	352.7	269.2	302.5	-	227.2	352.8	270.1	302.9	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C3-632AXSP06	215.1	340.5	258.6	291.7	-	217	340.4	259.5	292	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C4-425AXSP04	174.9	293.2	218	248.9	-	179.3	294.9	220.5	250.8	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550C4-432AXSP06	177.8	287.2	215.8	244.9	-	179.4	287.1	216.3	244.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550C4-525AXSP06	211.9	336.2	255.1	287.6	-	214	336.3	255.7	288	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C4-532AXSP06	199.4	318.7	240.8	272.7	-	201.1	318.7	241.3	272.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C4-625AXSP06	225.2	352.7	269.2	302.5	-	227.2	352.8	270.1	302.9	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C4-632AXSP06	215.1	340.5	258.6	291.7	-	217	340.4	259.5	292	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C5-425AXSP04	174.9	293.2	218	248.9	-	179.3	294.9	220.5	250.8	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550C5-432AXSP06	177.8	287.2	215.8	244.9	-	179.4	287.1	216.3	244.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550C5-525AXSP06	211.9	336.2	255.1	287.6	-	214	336.3	255.7	288	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C5-532AXSP06	199.4	318.7	240.8	272.7	-	201.1	318.7	241.3	272.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C5-625AXSP06	225.2	352.7	269.2	302.5	-	227.2	352.8	270.1	302.9	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C5-632AXSP06	215.1	340.5	258.6	291.7	-	217	340.4	259.5	292	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C8-425AXSP04	174.9	293.2	218	248.9	-	179.3	294.9	220.5	250.8	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550C8-432AXSP06	177.8	287.2	215.8	244.9	-	179.4	287.1	216.3	244.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550C8-525AXSP06	211.9	336.2	255.1	287.6	-	214	336.3	255.7	288	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C8-532AXSP06	199.4	318.7	240.8	272.7	-	201.1	318.7	241.3	272.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C8-625AXSP06	225.2	352.7	269.2	302.5	-	227.2	352.8	270.1	302.9	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C8-632AXSP06	215.1	340.5	258.6	291.7	-	217	340.4	259.5	292	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C9-425AXSP04	174.9	293.2	218	248.9	-	179.3	294.9	220.5	250.8	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550C9-432AXSP06	177.8	287.2	215.8	244.9	-	179.4	287.1	216.3	244.9	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550C9-525AXSP06	211.9	336.2	255.1	287.6	-	214	336.3	255.7	288	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C9-532AXSP06	199.4	318.7	240.8	272.7	-	201.1	318.7	241.3	272.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550C9-625AXSP06	225.2	352.7	269.2	302.5	-	227.2	352.8	270.1	302.9	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550C9-632AXSP06	215.1	340.5	258.6	291.7	-	217	340.4	259.5	292	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550K2-425AXSP04	167.3	281	208.9	238.5	489	171.4	282.2	211.2	240	486.3	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550K2-432AXSP06	170.7	275.3	207	234.9	-	172.1	274.8	207.5	234.7	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550K2-525AXSP06	203.6	322.7	244.9	276.4	-	205.4	322	245.3	276.1	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550K2-532AXSP06	191.5	305.7	231.1	261.5	-	192.9	305.3	231.7	261	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550K2-625AXSP06	217.3	339.7	259.3	291.6	-	219	339.4	259.9	291.7	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550K2-632AXSP06	207.1	327.1	248.9	280.6	-	208.8	326.7	249.1	280.1	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB550K3-425AXSP04	167.3	281	208.9	238.5	489	171.4	282.2	211.2	240	486.3	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB550K3-432AXSP06	170.7	275.3	207	234.9	-	172.1	274.8	207.5	234.7	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB550K3-525AXSP06	203.6	322.7	244.9	276.4	-	205.4	322	245.3	276.1	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550K3-532AXSP06	191.5	305.7	231.1	261.5	-	192.9	305.3	231.7	261	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB550K3-625AXSP06	217.3</																		

EAW-FD1554ZB750K2-625AXSP06	227.8	357.6	272.4	306.7	-	230	357.4	273.6	306.8	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K2-632AXSP06	217.8	344.5	261.6	295.1	-	219.5	344.5	262.5	295.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K3-425AXSP04	177.1	296.6	220.4	251.7	-	181.5	298.5	223	253.7	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K3-432AXSP04	162.9	276.5	204.8	234.3	484.2	167.2	278.1	207	236.2	482.7	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K3-525AXSP06	214.3	340.3	258.1	291	-	216.6	340	258.8	291.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K3-532AXSP06	201.8	322.4	243.4	275.8	-	203.4	322.5	244.1	275.7	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K3-625AXSP06	227.8	357.6	272.4	306.7	-	230	357.4	273.6	306.8	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K3-632AXSP06	217.8	344.5	261.6	295.1	-	219.5	344.5	262.5	295.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K4-425AXSP04	177.1	296.6	220.4	251.7	-	181.5	298.5	223	253.7	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K4-432AXSP04	162.9	276.5	204.8	234.3	484.2	167.2	278.1	207	236.2	482.7	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K4-525AXSP06	214.3	340.3	258.1	291	-	216.6	340	258.8	291.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K4-532AXSP06	201.8	322.4	243.4	275.8	-	203.4	322.5	244.1	275.7	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K4-625AXSP06	227.8	357.6	272.4	306.7	-	230	357.4	273.6	306.8	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K4-632AXSP06	217.8	344.5	261.6	295.1	-	219.5	344.5	262.5	295.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K5-425AXSP04	177.1	296.6	220.4	251.7	-	181.5	298.5	223	253.7	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K5-432AXSP04	162.9	276.5	204.8	234.3	484.2	167.2	278.1	207	236.2	482.7	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K5-525AXSP06	214.3	340.3	258.1	291	-	216.6	340	258.8	291.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K5-532AXSP06	201.8	322.4	243.4	275.8	-	203.4	322.5	244.1	275.7	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K5-625AXSP06	227.8	357.6	272.4	306.7	-	230	357.4	273.6	306.8	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K5-632AXSP06	217.8	344.5	261.6	295.1	-	219.5	344.5	262.5	295.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K8-425AXSP04	177.1	296.6	220.4	251.7	-	181.5	298.5	223	253.7	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K8-432AXSP04	162.9	276.5	204.8	234.3	484.2	167.2	278.1	207	236.2	482.7	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K8-532AXSP06	201.8	322.4	243.4	275.8	-	203.4	322.5	244.1	275.7	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K8-632AXSP06	227.8	357.6	272.4	306.7	-	230	357.4	273.6	306.8	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K8-632AXSP06	217.8	344.5	261.6	295.1	-	219.5	344.5	262.5	295.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K9-425AXSP04	177.1	296.6	220.4	251.7	-	181.5	298.5	223	253.7	-	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K9-432AXSP04	162.9	276.5	204.8	234.3	484.2	167.2	278.1	207	236.2	482.7	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750K9-525AXSP06	214.3	340.3	258.1	291	-	216.6	340	258.8	291.6	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750K9-632AXSP06	227.8	357.6	272.4	306.7	-	230	357.4	273.6	306.8	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750K9-632AXSP06	217.8	344.5	261.6	295.1	-	219.5	344.5	262.5	295.4	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750R3-425AXSP04	173.4	291	216.1	246.9	506.6	177.8	292.7	218.5	248.8	504.4	304	15.2	4"	244	13.1	3"	365	21.4	4"
EAW-FD1554ZB750R3-432AXSP06	176.6	285.1	214.4	243.2	-	178.2	285.2	215	243.4	-	203	22.5	3"	162	14.9	3"	244	31.7	3"
EAW-FD1554ZB750R3-532AXSP06	210.2	332.8	252.6	285.2	-	211.9	332.9	253.6	285.1	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750R3-532AXSP06	197.8	316.2	238.6	270.2	-	199.7	315.6	239.6	270	-	254	24.3	3"	203	16	3"	304	29.4	4"
EAW-FD1554ZB750R3-632AXSP06	223.5	349.9	267.2	300.2	-	225.5	349.5	267.7	300.6	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZB750R3-632AXSP06	213.5	337.2	256.2	289	-	215.4	337	257	289.1	-	304	21.7	4"	244	17.4	3"	365	30.4	4"
EAW-FD1554ZK370C2-425AXSP04	174.1	287	214.8	244.2	494.9	177.3	287.8	216.2	244.9	491	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK370C2-432AXSP06	175.4	280.7	211.7	239.6	-	176.2	279.5	211.6	239.1	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK370C2-525AXSP06	208.4	326.8	249.3	280.3	-	209.5	325.7	249.2	279.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C2-532AXSP06	196.6	311.3	236.2	266.2	-	197.6	309.8	235.9	265.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C2-625AXSP06	221.3	342.8	263.2	295.1	-	222.6	341.8	263.1	294	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C2-632AXSP06	212.4	332.1	253.4	285.1	-	213.4	330.7	253.2	284.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C4-425AXSP04	174.1	287	214.8	244.2	494.9	177.3	287.8	216.2	244.9	491	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK370C4-432AXSP06	175.4	280.7	211.7	239.6	-	176.2	279.5	211.6	239.1	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK370C4-525AXSP06	208.4	326.8	249.3	280.3	-	209.5	325.7	249.2	279.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C4-532AXSP06	196.6	311.3	236.2	266.2	-	197.6	309.8	235.9	265.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C4-625AXSP06	221.3	342.8	263.2	295.1	-	222.6	341.8	263.1	294	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C4-632AXSP06	212.4	332.1	253.4	285.1	-	213.4	330.7	253.2	284.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C5-425AXSP04	174.1	287	214.8	244.2	494.9	177.3	287.8	216.2	244.9	491	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK370C5-432AXSP06	175.4	280.7	211.7	239.6	-	176.2	279.5	211.6	239.1	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK370C5-525AXSP06	208.4	326.8	249.3	280.3	-	209.5	325.7	249.2	279.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C5-532AXSP06	196.6	311.3	236.2	266.2	-	197.6	309.8	235.9	265.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C5-625AXSP06	221.3	342.8	263.2	295.1	-	222.6	341.8	263.1	294	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C5-632AXSP06	212.4	332.1	253.4	285.1	-	213.4	330.7	253.2	284.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C8-425AXSP04	174.1	287	214.8	244.2	494.9	177.3	287.8	216.2	244.9	491	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK370C8-432AXSP06	175.4	280.7	211.7	239.6	-	176.2	279.5	211.6	239.1	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK370C8-525AXSP06	208.4	326.8	249.3	280.3	-	209.5	325.7	249.2	279.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C8-532AXSP06	196.6	311.3	236.2	266.2	-	197.6	309.8	235.9	265.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370C8-625AXSP06	221.3	342.8	263.2	295.1	-	222.6	341.8	263.1	294	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370C8-632AXSP06	212.4	332.1	253.4	285.1	-	213.4	330.7	253.2	284.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK370K2-425AXSP04	168.2	277.9	208	236.3	478.3	171.2	277.8	209	237.1	474.7	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK370K2-432AXSP06	169.9	271.3	204.9	231.5	-	170.4	269.9	204.5	230.6	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK370K2-525AXSP06	202.7	317.3	241.9	272.3	-	203.4	315.7	241.5	271.2	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370K2-532AXSP06	190.7	301.3	228.9	257.8	-	191.6	299.7	228.6	256.8	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK370K2-625AXSP06	216.2	334.6	256.7	287.7	-	216.9</													

EAW-FD1554ZK400C9-532AXSP06	196.6	311.3	236.2	266.2	-	197.6	309.8	235.9	265.6	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400C9-625AXSP06	221.3	342.8	263.2	295.1	-	222.6	341.8	263.1	294	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400C9-632AXSP06	212.4	332.1	253.4	285.1	-	213.4	330.7	253.2	284.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400K3-425AXSP04	168.2	277.9	208	236.3	478.3	171.2	277.8	209	237.1	474.7	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK400K3-432AXSP06	169.9	271.3	204.9	231.5	-	170.4	269.9	204.5	230.6	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK400K3-525AXSP06	202.7	317.3	241.9	272.3	-	203.4	315.7	241.5	271.2	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400K3-532AXSP06	190.7	301.3	228.9	257.8	-	191.6	299.7	228.6	256.8	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400K3-625AXSP06	216.2	334.6	256.7	287.7	-	216.9	332.7	256.3	286.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400K3-632AXSP06	206.4	322.3	246.2	276.9	-	207	320.9	245.6	275.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400K9-425AXSP04	168.2	277.9	208	236.3	478.3	171.2	277.8	209	237.1	474.7	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK400K9-432AXSP06	169.9	271.3	204.9	231.5	-	170.4	269.9	204.5	230.6	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK400K9-525AXSP06	202.7	317.3	241.9	272.3	-	203.4	315.7	241.5	271.2	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400K9-532AXSP06	190.7	301.3	228.9	257.8	-	191.6	299.7	228.6	256.8	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400K9-625AXSP06	216.2	334.6	256.7	287.7	-	216.9	332.7	256.3	286.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400K9-632AXSP06	206.4	322.3	246.2	276.9	-	207	320.9	245.6	275.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400R3-425AXSP04	170.6	281.4	210.5	239.6	484.7	173.6	282	212	240.1	481.3	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK400R3-432AXSP06	172.1	274.9	207.6	234.8	-	172.7	273.6	207.3	234.1	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK400R3-525AXSP06	205.1	321.4	244.9	275.7	-	206	319.9	244.6	274.7	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400R3-532AXSP06	193.1	305.3	231.9	261.2	-	193.9	304	231.4	260.4	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK400R3-625AXSP06	218.6	338.6	259.6	291	-	219.5	336.7	259.3	290.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK400R3-632AXSP06	208.9	326.3	249.2	280.3	-	209.6	325	248.7	279.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550B3-425AXSP04	182.1	300.6	224.4	255.4	-	185.6	301.1	226.4	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550B3-432AXSP04	168.5	281	209.1	238.6	488.2	171.9	281.7	210.9	239.7	485.5	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550B3-525AXSP06	216.7	340.5	259.3	291.8	-	218.3	339.6	259.5	291.7	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550B3-532AXSP06	205.2	324.7	246.3	277.8	-	206.4	323.9	246.7	277.8	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550B3-625AXSP06	229	355.4	272.1	305.2	-	230.6	354.6	272.6	305.2	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550B3-632AXSP06	220.3	345.1	263.4	296.1	-	222	344.7	263.5	296	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C2-425AXSP04	193.8	319.3	238.2	271.2	-	197.3	319.8	240	272.1	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C2-432AXSP04	178.2	296.5	220.6	251.7	-	181.5	297.2	222.3	252.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C2-525AXSP06	212.7	348.1	261.5	296.8	595.9	216.8	349.4	263.6	298.3	592.2	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK550C2-532AXSP06	217.9	345.6	261.8	295.6	-	218.8	344.8	261.8	295.3	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550C2-625AXSP06	247.2	384.4	294.4	330.6	-	248.8	383.7	294.8	330.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C2-632AXSP06	235.9	370.3	281.9	317.7	-	237	369.4	282.1	316.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C3-425AXSP04	193.8	319.3	238.2	271.2	-	197.3	319.8	240	272.1	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C3-432AXSP04	178.2	296.5	220.6	251.7	-	181.5	297.2	222.3	252.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C3-525AXSP06	212.7	348.1	261.5	296.8	595.9	216.8	349.4	263.6	298.3	592.2	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK550C3-532AXSP06	217.9	345.6	261.8	295.6	-	218.8	344.8	261.8	295.3	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550C3-625AXSP06	247.2	384.4	294.4	330.6	-	248.8	383.7	294.8	330.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C3-632AXSP06	235.9	370.3	281.9	317.7	-	237	369.4	282.1	316.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C4-425AXSP04	193.8	319.3	238.2	271.2	-	197.3	319.8	240	272.1	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C4-432AXSP04	178.2	296.5	220.6	251.7	-	181.5	297.2	222.3	252.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C4-525AXSP06	212.7	348.1	261.5	296.8	595.9	216.8	349.4	263.6	298.3	592.2	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK550C4-532AXSP06	217.9	345.6	261.8	295.6	-	218.8	344.8	261.8	295.3	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550C4-625AXSP06	247.2	384.4	294.4	330.6	-	248.8	383.7	294.8	330.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C4-632AXSP06	235.9	370.3	281.9	317.7	-	237	369.4	282.1	316.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C5-425AXSP04	193.8	319.3	238.2	271.2	-	197.3	319.8	240	272.1	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C5-432AXSP04	178.2	296.5	220.6	251.7	-	181.5	297.2	222.3	252.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550C5-525AXSP06	212.7	348.1	261.5	296.8	595.9	216.8	349.4	263.6	298.3	592.2	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK550C5-532AXSP06	217.9	345.6	261.8	295.6	-	218.8	344.8	261.8	295.3	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550C5-625AXSP06	247.2	384.4	294.4	330.6	-	248.8	383.7	294.8	330.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550C5-632AXSP06	235.9	370.3	281.9	317.7	-	237	369.4	282.1	316.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550K3-425AXSP04	193.8	319.3	238.2	271.2	-	197.3	319.8	240	272.1	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550K3-432AXSP04	178.2	296.5	220.6	251.7	-	181.5	297.2	222.3	252.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550K3-525AXSP06	212.7	348.1	261.5	296.8	595.9	216.8	349.4	263.6	298.3	592.2	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK550K3-532AXSP06	217.9	345.6	261.8	295.6	-	218.8	344.8	261.8	295.3	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550K3-625AXSP06	247.2	384.4	294.4	330.6	-	248.8	383.7	294.8	330.3	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550K3-632AXSP06	235.9	370.3	281.9	317.7	-	237	369.4	282.1	316.7	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550K4-425AXSP04	185.1	305.3	227.9	259.3	-	188.4	305.4	229.6	260.3	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550K4-432AXSP04	170.4	283.8	211.3	241.1	493.5	173.6	284.7	212.8	241.9	490	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550K4-525AXSP06	221.8	348.5	265.6	298.9	-	223.1	347.4	265.6	298.2	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550K4-532AXSP06	208.5	330.2	250.7	282.9	-	209.6	329.3	250.6	281.9	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550K4-625AXSP06	237	368.3	282.1	316.5	-	238.2	366.7	281.7	315.5	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550K4-632AXSP06	225.8	354.2	270.1	303.7	-	226.9	352.8	269.5	302.9	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550K5-425AXSP04	185.1	305.3	227.9	259.3	-	188.4	305.4	229.6	260.3	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK550K5-432AXSP04	170.4	283.8	21																

EAW-FD1554ZK550R3-525AXSP06	226.2	355.9	271	305.1	-	227.6	354.8	270.7	304.5	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550R3-532AXSP06	212.5	337.1	255.8	288.6	-	213.9	335.8	255.7	287.8	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK550R3-625AXSP06	242	375.8	287.6	322.9	-	243	374.4	287.4	322	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK550R3-632AXSP06	230.2	360.9	275.5	309.8	-	231.5	359.7	275	309.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750C4-425AXSP06	218.5	-	263.6	297.9	-	220.1	-	263.9	298	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK750C4-432AXSP06	202.2	324.8	244.5	277.1	-	203.5	324	244.8	276.8	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK750C4-525AXSP06	241.1	380.2	288.6	325.3	-	242.6	379.7	289.2	325.7	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750C4-532AXSP06	226.7	360.5	273.1	308	-	228.2	360	273.2	307.9	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750C4-632AXSP06	244.6	384.9	293	329.9	-	246.3	384.1	293.4	329.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750C5-425AXSP06	218.5	-	263.6	297.9	-	220.1	-	263.9	298	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK750C5-432AXSP06	202.2	324.8	244.5	277.1	-	203.5	324	244.8	276.8	-	203	24.5	3"	162	16.2	3"	244	34.4	3"
EAW-FD1554ZK750C5-525AXSP06	241.1	380.2	288.6	325.3	-	242.6	379.7	289.2	325.7	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750C5-532AXSP06	226.7	360.5	273.1	308	-	228.2	360	273.2	307.9	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750C5-632AXSP06	244.6	384.9	293	329.9	-	246.3	384.1	293.4	329.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K2-425AXSP04	196.5	323.5	241.4	274.9	-	200.1	324.4	243.5	276.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K2-432AXSP04	181	301.4	224.2	255.7	-	184.4	302.1	226	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K2-525AXSP04	215.1	352.5	264.6	300.4	602.8	219.4	353.8	266.8	302	600.1	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750K2-532AXSP06	220.6	350.3	265.2	299.5	-	221.9	349.3	265.5	299	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750K2-625AXSP06	250.3	389.4	298.1	334.8	-	252	388.8	298.1	334.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K2-632AXSP06	238.6	375	285.3	321.6	-	239.8	374.1	285.6	320.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K3-425AXSP04	196.5	323.5	241.4	274.9	-	200.1	324.4	243.5	276.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K3-432AXSP04	181	301.4	224.2	255.7	-	184.4	302.1	226	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K3-525AXSP04	215.1	352.5	264.6	300.4	602.8	219.4	353.8	266.8	302	600.1	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750K3-532AXSP06	220.6	350.3	265.2	299.5	-	221.9	349.3	265.5	299	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750K3-625AXSP06	250.3	389.4	298.1	334.8	-	252	388.8	298.1	334.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K3-632AXSP06	238.6	375	285.3	321.6	-	239.8	374.1	285.6	320.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K4-425AXSP04	196.5	323.5	241.4	274.9	-	200.1	324.4	243.5	276.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K4-432AXSP04	181	301.4	224.2	255.7	-	184.4	302.1	226	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K4-525AXSP04	215.1	352.5	264.6	300.4	602.8	219.4	353.8	266.8	302	600.1	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750K4-532AXSP06	220.6	350.3	265.2	299.5	-	221.9	349.3	265.5	299	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750K4-625AXSP06	250.3	389.4	298.1	334.8	-	252	388.8	298.1	334.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K4-632AXSP06	238.6	375	285.3	321.6	-	239.8	374.1	285.6	320.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K5-425AXSP04	196.5	323.5	241.4	274.9	-	200.1	324.4	243.5	276.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K5-432AXSP04	181	301.4	224.2	255.7	-	184.4	302.1	226	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K5-525AXSP04	215.1	352.5	264.6	300.4	602.8	219.4	353.8	266.8	302	600.1	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750K5-532AXSP06	220.6	350.3	265.2	299.5	-	221.9	349.3	265.5	299	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750K5-625AXSP06	250.3	389.4	298.1	334.8	-	252	388.8	298.1	334.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K5-632AXSP06	238.6	375	285.3	321.6	-	239.8	374.1	285.6	320.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K8-425AXSP04	196.5	323.5	241.4	274.9	-	200.1	324.4	243.5	276.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K8-432AXSP04	181	301.4	224.2	255.7	-	184.4	302.1	226	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K8-525AXSP04	215.1	352.5	264.6	300.4	602.8	219.4	353.8	266.8	302	600.1	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750K8-532AXSP06	220.6	350.3	265.2	299.5	-	221.9	349.3	265.5	299	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750K8-625AXSP06	250.3	389.4	298.1	334.8	-	252	388.8	298.1	334.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K8-632AXSP06	238.6	375	285.3	321.6	-	239.8	374.1	285.6	320.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K9-425AXSP04	196.5	323.5	241.4	274.9	-	200.1	324.4	243.5	276.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K9-432AXSP04	181	301.4	224.2	255.7	-	184.4	302.1	226	256.8	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750K9-525AXSP04	215.1	352.5	264.6	300.4	602.8	219.4	353.8	266.8	302	600.1	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750K9-532AXSP06	220.6	350.3	265.2	299.5	-	221.9	349.3	265.5	299	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750K9-625AXSP06	250.3	389.4	298.1	334.8	-	252	388.8	298.1	334.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750K9-632AXSP06	238.6	375	285.3	321.6	-	239.8	374.1	285.6	320.6	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750R3-425AXSP04	192.4	316.5	236.4	269.3	-	196	317.8	238.4	270.5	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750R3-432AXSP04	177.3	295.2	219.7	250.7	-	180.8	296.2	221.7	252	-	304	16.5	4"	244	14	3"	365	23.2	4"
EAW-FD1554ZK750R3-525AXSP04	210.7	345.2	259	294.4	589.6	214.7	345.8	261	295.3	586	378	17.8	4"	302	11.7	4"	453	21.2	(2) 4"
EAW-FD1554ZK750R3-532AXSP06	216.1	342.6	259.7	293.2	-	217.3	342.1	259.9	293.1	-	254	26.3	3"	203	17.3	3"	304	32.2	4"
EAW-FD1554ZK750R3-625AXSP06	244.8	381	291.4	327.2	-	246.3	380.2	291.7	326.9	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1554ZK750R3-632AXSP06	233.6	366.7	279.6	314.6	-	235.1	365.7	279.4	314.1	-	304	23.6	4"	244	18.7	3"	365	33.2	4"
EAW-FD1555PB370C2-425AXSP04	192.5	312.8	234.5	266.3	-	195.2	313.5	236.2	267.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD1555PB370C2-432AXSP04	179.2	293.1	219.1	249.3	-	181.8	294	220.5	250.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD1555PB370C2-525AXSP04	210	337.5	255.1	288.4	-	213.6	338.6	256.9	289.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD1555PB370C2-532AXSP04	198.6	322.9	242.9	275.5	552	202	323.8	244.6	276.2	548.8	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD1555PB370C2-625AXSP06	236.4	364.5	279.9	313.6	-	237.8	364.5	280.7	313.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD1555PB370C2-632AXSP06	228	355.4	271.7	305.4	-	229.3	355	271.8	304.9	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD1555PB370C4-425AXSP04	192.5	312.8	234.5	266.3	-	195.2	313.5	236.2	267.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD1555PB370C4-432AXSP04	179.2	293.1	219.1	249.3	-	181.8	294	220.5	250.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD1555PB370C4-525AXSP04	210	337.5	255.1	288.4	-	213.6	338.6	256.9	289.7	-	338	18.7	4"	270	12.3				



EAW-FD155SPB370K8-532AXSP04	194.5	316.4	238.2	270.1	540.3	197.3	317	239.3	270.5	536.7	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB370K8-625AXSP06	235.6	363.8	279.4	312.9	-	236.4	362.2	279	311.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB370K8-632AXSP06	225.5	351.2	268.6	301.9	-	226.4	349.7	268.3	300.9	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400B3-425AXSP04	185.6	301.2	226	256.2	-	188.5	302	227.5	257.8	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400B3-432AXSP04	173.1	283.3	212	241	-	175.8	284.3	213.4	241.9	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400B3-525AXSP04	-	-	-	-	-	-	-	-	-	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400B3-532AXSP04	190.8	310.6	233.6	264.8	530.7	194.1	311.6	235.4	266.1	528	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB400B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB400C3-425AXSP04	192.5	312.8	234.5	266.3	-	195.2	313.5	236.2	267.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400C3-432AXSP04	179.2	293.1	219.1	249.3	-	181.8	294	220.5	250.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400C3-525AXSP04	210	337.5	255.1	288.4	-	213.6	338.6	256.9	289.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400C3-532AXSP04	198.6	322.9	242.9	275.5	552	202	323.8	244.6	276.2	548.8	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400C3-625AXSP06	236.4	364.5	279.9	313.6	-	237.8	364.5	280.7	313.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400C3-632AXSP06	228	355.4	271.7	305.4	-	229.3	355	271.8	304.9	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400C9-425AXSP04	192.5	312.8	234.5	266.3	-	195.2	313.5	236.2	267.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400C9-432AXSP04	179.2	293.1	219.1	249.3	-	181.8	294	220.5	250.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400C9-525AXSP04	210	337.5	255.1	288.4	-	213.6	338.6	256.9	289.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400C9-532AXSP04	198.6	322.9	242.9	275.5	552	202	323.8	244.6	276.2	548.8	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400C9-625AXSP06	236.4	364.5	279.9	313.6	-	237.8	364.5	280.7	313.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400C9-632AXSP06	228	355.4	271.7	305.4	-	229.3	355	271.8	304.9	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400K3-425AXSP04	188.4	305.8	229.3	260.6	-	190.7	305.7	230.5	260.8	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400K3-432AXSP04	174.6	285.6	213.6	242.9	-	177.1	285.9	214.8	243.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400K3-525AXSP04	207.3	333.4	251.7	284.6	-	210.1	333.4	253.1	285.4	561.3	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400K3-532AXSP04	194.5	316.4	238.2	270.1	540.3	197.3	317	239.3	270.5	536.7	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400K3-625AXSP06	235.6	363.8	279.4	312.9	-	236.4	362.2	279	311.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400K3-632AXSP06	225.5	351.2	268.6	301.9	-	226.4	349.7	268.3	300.9	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400K9-425AXSP04	188.4	305.8	229.3	260.6	-	190.7	305.7	230.5	260.8	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400K9-432AXSP04	174.6	285.6	213.6	242.9	-	177.1	285.9	214.8	243.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400K9-525AXSP04	207.3	333.4	251.7	284.6	-	210.1	333.4	253.1	285.4	561.3	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400K9-532AXSP04	194.5	316.4	238.2	270.1	540.3	197.3	317	239.3	270.5	536.7	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400K9-625AXSP06	235.6	363.8	279.4	312.9	-	236.4	362.2	279	311.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400K9-632AXSP06	225.5	351.2	268.6	301.9	-	226.4	349.7	268.3	300.9	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400R3-425AXSP04	190.3	309	231.8	263.2	-	192.8	309	232.9	264.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400R3-432AXSP04	176.5	288.6	215.9	245.7	-	179.1	289.1	217	246.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB400R3-525AXSP04	209.3	336.3	254.2	287.4	-	212.3	337	255.3	288.4	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400R3-532AXSP04	196.6	319.6	240.4	272.7	546.8	199.5	320.3	241.6	273.2	542.5	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB400R3-625AXSP06	237.7	367.2	282	315.8	-	238.6	365.7	281.6	314.8	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB400R3-632AXSP06	227.6	354.7	271.2	304.4	-	228.3	353.3	270.6	303.5	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB50B3-425AXSP04	198.6	322.7	241.8	274.9	-	201.7	324.1	244.1	276.6	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB50B3-432AXSP04	185.3	303.2	226.6	257.9	-	188.2	304.5	228.4	259.4	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB50B3-525AXSP02	-	-	-	-	-	-	-	-	-	-	676	10.7	(2) 4"	541	7	(2) 4"	812	15.1	(2) 4"
EAW-FD155SPB50B3-532AXSP04	-	-	-	-	-	208	333.6	252.1	284.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB50B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	12	(2) 4"	649	7.8	(2) 4"	974	13.7	(3) 4"
EAW-FD155SPB50B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550C2-425AXSP04	212.3	345.8	258.8	294.3	-	215.6	347.2	261.1	296	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C2-432AXSP04	196.8	322.6	240.8	274.3	-	199.8	323.7	242.7	275.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C2-525AXSP04	233.3	375.2	283	320.2	-	236.8	376.8	285	322	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C2-532AXSP04	219.8	356.9	267.8	304.1	-	223.2	357.9	269.9	305.3	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C2-632AXSP04	-	-	-	-	-	239	381.4	288.8	325.9	642.6	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550C3-425AXSP04	212.3	345.8	258.8	294.3	-	215.6	347.2	261.1	296	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C3-432AXSP04	196.8	322.6	240.8	274.3	-	199.8	323.7	242.7	275.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C3-525AXSP04	233.3	375.2	283	320.2	-	236.8	376.8	285	322	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C3-532AXSP04	219.8	356.9	267.8	304.1	-	223.2	357.9	269.9	305.3	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C3-632AXSP04	-	-	-	-	-	239	381.4	288.8	325.9	642.6	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550C4-425AXSP04	212.3	345.8	258.8	294.3	-	215.6	347.2	261.1	296	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C4-432AXSP04	196.8	322.6	240.8	274.3	-	199.8	323.7	242.7	275.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C4-525AXSP04	233.3	375.2	283	320.2	-	236.8	376.8	285	322	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C4-532AXSP04	219.8	356.9	267.8	304.1	-	223.2	357.9	269.9	305.3	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C4-632AXSP04	-	-	-	-	-	239	381.4	288.8	325.9	642.6	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550C5-425AXSP04	212.3	345.8	258.8	294.3	-	215.6	347.2	261.1	296	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C5-432AXSP04	196.8	322.6	240.8	274.3	-	199.8	323.7	242.7	275.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C5-525AXSP04	233.3	375.2	283	320.2	-	236.8	376.8	285	322	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C5-532AXSP04	219.8	356.9	267.8	304.1	-	223.2	357.9	269.9	305.3	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550C5-632AXSP04	-	-	-	-	-	239	381.4	288.8	325.9	642.6	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550C8-425AXSP04	212.3	345.8	258.8	294.3	-	215.6	347.2	261.1	296	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550C8-432AXSP04	196.8	322.6	240.8	274.3	-	199.8	323.7	242.7	275.3	-	270	17.7	4"	216	14.1	3"</			

EAW-FD155SPB550K8-425AXSP04	204.5	332.9	249.3	283.2	-	207.3	333.3	250.8	284.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550K8-432AXSP04	189.4	310.2	231.7	263.6	-	191.9	310.8	233.1	264.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550K8-525AXSP04	225.5	363	273.4	309.6	-	228.8	363.7	275.1	310.6	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550K8-532AXSP04	211.8	344.3	258.5	293.1	-	215	345	260.2	294.2	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550K8-625AXSP04	239.1	381.8	289.5	327.1	642.3	242.7	382.6	291.6	328.2	638.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550K8-632AXSP06	244.4	381.8	291.6	328.1	-	245.5	380.9	291.3	327	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB550K9-425AXSP04	204.5	332.9	249.3	283.2	-	207.3	333.3	250.8	284.1	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550K9-432AXSP04	189.4	310.2	231.7	263.6	-	191.9	310.8	233.1	264.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550K9-525AXSP04	225.5	363	273.4	309.6	-	228.8	363.7	275.1	310.6	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550K9-532AXSP04	211.8	344.3	258.5	293.1	-	215	345	260.2	294.2	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550K9-625AXSP04	239.1	381.8	289.5	327.1	642.3	242.7	382.6	291.6	328.2	638.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550K9-632AXSP06	244.4	381.8	291.6	328.1	-	245.5	380.9	291.3	327	-	270	25.6	4"	216	19.3	3"	325	35.9	4"
EAW-FD155SPB550R3-425AXSP04	208	338.8	253.7	288.3	-	211	339.5	255.4	289.2	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550R3-432AXSP04	192.5	315.6	235.7	268.3	-	195.5	316.3	237.2	269.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB550R3-525AXSP04	229.4	369.1	278.2	315.2	-	232.9	370	280	316.4	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550R3-532AXSP04	215.3	349.9	262.8	298.3	-	219	351.1	264.6	299.8	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB550R3-625AXSP04	243.1	388.6	294.4	332.8	654	246.8	389.5	296.2	333.5	650.2	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB550R3-632AXSP06	231.3	374	282.2	319.3	634.7	235	374.6	283.8	320.3	630.8	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K2-425AXSP04	214.5	349.7	261.9	297.6	-	217.9	351.2	264	299.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K2-432AXSP04	198.8	325.9	243.4	277.3	-	201.7	327.2	245.1	278.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K2-525AXSP04	236.2	380.3	286.2	324.4	-	239.7	381.7	288.5	326.1	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K2-532AXSP04	222.2	360.8	270.8	307.3	-	225.8	361.9	272.8	308.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K2-625AXSP04	250.1	399.7	303	342.1	673.5	254.3	400.7	304.8	343.3	670.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K2-632AXSP06	238.3	384.7	290.4	328.7	653.7	242	385.8	292.4	330.1	650.5	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K3-425AXSP04	214.5	349.7	261.9	297.6	-	217.9	351.2	264	299.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K3-432AXSP04	198.8	325.9	243.4	277.3	-	201.7	327.2	245.1	278.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K3-525AXSP04	236.2	380.3	286.2	324.4	-	239.7	381.7	288.5	326.1	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K3-532AXSP04	222.2	360.8	270.8	307.3	-	225.8	361.9	272.8	308.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K3-625AXSP04	250.1	399.7	303	342.1	673.5	254.3	400.7	304.8	343.3	670.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K3-632AXSP06	238.3	384.7	290.4	328.7	653.7	242	385.8	292.4	330.1	650.5	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K4-425AXSP04	214.5	349.7	261.9	297.6	-	217.9	351.2	264	299.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K4-432AXSP04	198.8	325.9	243.4	277.3	-	201.7	327.2	245.1	278.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K4-525AXSP04	236.2	380.3	286.2	324.4	-	239.7	381.7	288.5	326.1	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K4-532AXSP04	222.2	360.8	270.8	307.3	-	225.8	361.9	272.8	308.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K4-625AXSP04	250.1	399.7	303	342.1	673.5	254.3	400.7	304.8	343.3	670.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K4-632AXSP06	238.3	384.7	290.4	328.7	653.7	242	385.8	292.4	330.1	650.5	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K5-425AXSP04	214.5	349.7	261.9	297.6	-	217.9	351.2	264	299.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K5-432AXSP04	198.8	325.9	243.4	277.3	-	201.7	327.2	245.1	278.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K5-525AXSP04	236.2	380.3	286.2	324.4	-	239.7	381.7	288.5	326.1	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K5-532AXSP04	222.2	360.8	270.8	307.3	-	225.8	361.9	272.8	308.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K5-625AXSP04	250.1	399.7	303	342.1	673.5	254.3	400.7	304.8	343.3	670.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K5-632AXSP06	238.3	384.7	290.4	328.7	653.7	242	385.8	292.4	330.1	650.5	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K8-425AXSP04	214.5	349.7	261.9	297.6	-	217.9	351.2	264	299.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K8-432AXSP04	198.8	325.9	243.4	277.3	-	201.7	327.2	245.1	278.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K8-525AXSP04	236.2	380.3	286.2	324.4	-	239.7	381.7	288.5	326.1	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K8-532AXSP04	222.2	360.8	270.8	307.3	-	225.8	361.9	272.8	308.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K8-625AXSP04	250.1	399.7	303	342.1	673.5	254.3	400.7	304.8	343.3	670.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K8-632AXSP06	238.3	384.7	290.4	328.7	653.7	242	385.8	292.4	330.1	650.5	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K9-425AXSP04	214.5	349.7	261.9	297.6	-	217.9	351.2	264	299.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K9-432AXSP04	198.8	325.9	243.4	277.3	-	201.7	327.2	245.1	278.5	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750K9-525AXSP04	236.2	380.3	286.2	324.4	-	239.7	381.7	288.5	326.1	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K9-532AXSP04	222.2	360.8	270.8	307.3	-	225.8	361.9	272.8	308.7	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750K9-625AXSP04	250.1	399.7	303	342.1	673.5	254.3	400.7	304.8	343.3	670.3	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750K9-632AXSP06	238.3	384.7	290.4	328.7	653.7	242	385.8	292.4	330.1	650.5	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750R3-425AXSP04	210.5	342.5	256.8	292	-	213.7	343.8	258.8	293.2	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750R3-432AXSP04	195.2	320.1	238.9	272	-	198.2	320.8	240.6	273.3	-	270	17.7	4"	216	14.1	3"	325	24.8	4"
EAW-FD155SPB750R3-525AXSP04	231.8	372.5	280.7	318	-	235	373.7	282.7	319.5	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750R3-532AXSP04	217.9	353.7	265.5	301.4	-	221.3	355.2	267.5	303.2	-	338	18.7	4"	270	12.3	4"	406	26.2	4"
EAW-FD155SPB750R3-625AXSP04	245.3	391.6	296.7	335.4	659.4	249	392.5	298.8	336.5	656.2	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SPB750R3-632AXSP04	233.5	377.1	285	322.5	640.4	237.4	378.6	286.8	323.7	637.9	406	19.9	4"	325	13.1	4"	487	23.6	(2) 4"
EAW-FD155SZB370C2-425AXSP04	209.3	339.5	254.7	289.4	-	212	340	256.2	290.3	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB370C2-432AXSP04	194.3	317.7	237.5	270.4	-	196.9	317.8	239	270.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB370C2-525AXSP04	228.3	367.1	277.2	313.9	622.7	231.6	368	278.9	314.5	618.5	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB370C2-532AXSP04	214.9	350	263	298.8	597.4	218.3	350.1	264.8	299.3	593.6	378	19.4	4"	302	12.8	4"			

EAW-FD155S2B370K5-632AXSP06	244.4	380	290.6	326.4	-	245	378.3	290.2	325.2	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B370K8-425AXSP04	203.6	330	247.4	281	-	206	329.9	249	281.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B370K8-432AXSP04	188.2	308.1	230.5	262.1	-	190.7	307.7	231.5	262.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B370K8-525AXSP04	223	358.8	271.2	306.4	607.1	226	358.6	272.1	307.2	603	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B370K8-532AXSP06	226.2	355.8	270.6	304.9	-	226.8	354	270.2	303.6	-	254	28.8	3"	203	19	3"	304	35.6	4"
EAW-FD155S2B370K8-632AXSP06	255.7	394.1	303.1	339.3	-	256.5	392	302.2	337.7	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B370K8-632AXSP06	244.4	380	290.6	326.4	-	245	378.3	290.2	325.2	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400B3-425AXSP04	202.3	327.5	246.1	279.4	-	205.1	328.1	247.7	279.9	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400B3-432AXSP04	187.8	307.4	230.1	261.7	-	190.6	308.2	231.4	262.3	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400B3-525AXSP04	218.9	352.9	266.5	301.5	596.6	222.6	353.3	268.3	302.3	593.1	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400B3-532AXSP06	224.1	352.4	268.1	302	-	225.3	351.5	267.9	301.5	-	254	28.8	3"	203	19	3"	304	35.6	4"
EAW-FD155S2B400B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155S2B400B3-632AXSP06	240.3	373.2	285.6	320.7	-	241.2	372.2	285.7	320.1	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400C3-425AXSP04	209.3	339.5	254.7	289.4	-	212	340	256.2	290.3	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400C3-432AXSP04	194.3	317.7	237.5	270.4	-	196.9	317.8	239	270.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400C3-525AXSP04	228.3	367.1	277.2	313.9	622.7	231.6	368	278.9	314.5	618.5	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400C3-532AXSP04	214.9	350	263	298.8	597.4	218.3	350.1	264.8	299.3	593.6	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400C3-625AXSP06	259.6	399.9	307.4	344.2	-	261	399	307.5	343.6	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400C3-632AXSP06	249.9	388.4	297.2	333.9	-	250.7	387	297.1	333.1	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400C3-632AXSP06	209.3	339.5	254.7	289.4	-	212	340	256.2	290.3	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400C9-432AXSP04	194.3	317.7	237.5	270.4	-	196.9	317.8	239	270.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400C9-525AXSP04	228.3	367.1	277.2	313.9	622.7	231.6	368	278.9	314.5	618.5	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400C9-532AXSP04	214.9	350	263	298.8	597.4	218.3	350.1	264.8	299.3	593.6	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400C9-625AXSP06	259.6	399.9	307.4	344.2	-	261	399	307.5	343.6	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400C9-625AXSP06	249.9	388.4	297.2	333.9	-	250.7	387	297.1	333.1	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400C3-425AXSP04	203.6	330	247.4	281	-	206	329.9	249	281.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400K3-432AXSP04	188.2	308.1	230.5	262.1	-	190.7	307.7	231.5	262.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400K3-525AXSP04	223	358.8	271.2	306.4	607.1	226	358.6	272.1	307.2	603	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400K3-532AXSP06	226.2	355.8	270.6	304.9	-	226.8	354	270.2	303.6	-	254	28.8	3"	203	19	3"	304	35.6	4"
EAW-FD155S2B400K3-625AXSP06	255.7	394.1	303.1	339.3	-	256.5	392	302.2	337.7	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400K3-632AXSP06	244.4	380	290.6	326.4	-	245	378.3	290.2	325.2	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400K9-425AXSP04	203.6	330	247.4	281	-	206	329.9	249	281.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400K9-432AXSP04	188.2	308.1	230.5	262.1	-	190.7	307.7	231.5	262.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400K9-525AXSP04	223	358.8	271.2	306.4	607.1	226	358.6	272.1	307.2	603	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400K9-625AXSP06	226.2	355.8	270.6	304.9	-	226.8	354	270.2	303.6	-	254	28.8	3"	203	19	3"	304	35.6	4"
EAW-FD155S2B400K9-625AXSP06	255.7	394.1	303.1	339.3	-	256.5	392	302.2	337.7	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400K9-632AXSP06	244.4	380	290.6	326.4	-	245	378.3	290.2	325.2	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400R3-425AXSP04	205.9	333.5	250.8	284.4	-	208.4	334.1	252	284.9	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400R3-432AXSP04	190.5	312.1	233.3	265.4	-	193.1	312	234.6	265.9	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B400R3-525AXSP04	225.3	362.7	274	310.2	615	228.5	362.7	275.1	310.6	610.3	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B400R3-532AXSP06	228.7	359.4	273.7	308.4	-	229.4	358.3	273.4	307.2	-	254	28.8	3"	203	19	3"	304	35.6	4"
EAW-FD155S2B400R3-625AXSP06	258.4	397.9	305.9	342.5	-	259	396.4	305.1	341.5	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B400R3-632AXSP06	247	384.1	294.1	330.4	-	247.6	382.5	293.4	328.8	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B550B3-425AXSP04	217.3	352.6	264.7	300.7	-	220.6	354	266.5	301.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550B3-432AXSP04	202.5	331	247.3	281.5	-	205.3	331.8	248.9	282.4	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550B3-525AXSP04	236.1	379.9	286.4	324.5	-	239.7	381	288.9	325.9	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550B3-532AXSP04	223.1	362.6	273	309.2	620.2	226.7	363.9	274.7	310.7	618.1	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155S2B550B3-632AXSP06	-	-	-	-	-	258.8	400.7	306.8	344.1	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155S2B550C2-425AXSP04	231.4	376.5	282.1	320.5	-	234.6	377	283.9	322	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550C2-432AXSP04	214.1	350.5	261.7	298.1	-	216.8	351.2	263.3	298.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550C2-525AXSP04	254.2	409	308.3	349.3	-	258	410	310.3	350.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550C2-532AXSP04	238.6	387.9	291.2	330.1	-	242.1	388.2	293.1	331.4	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550C2-625AXSP04	270.2	431.6	327.2	369.8	726.2	274.6	433.1	329.5	370.9	722.6	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155S2B550C2-632AXSP04	257.4	416.5	314	355.8	706.5	261.9	417.1	316.2	356.8	702.2	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155S2B550C3-425AXSP04	231.4	376.5	282.1	320.5	-	234.6	377	283.9	322	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550C3-432AXSP04	214.1	350.5	261.7	298.1	-	216.8	351.2	263.3	298.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550C3-525AXSP04	254.2	409	308.3	349.3	-	258	410	310.3	350.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550C3-532AXSP04	238.6	387.9	291.2	330.1	-	242.1	388.2	293.1	331.4	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550C3-625AXSP04	270.2	431.6	327.2	369.8	726.2	274.6	433.1	329.5	370.9	722.6	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155S2B550C3-632AXSP04	257.4	416.5	314	355.8	706.5	261.9	417.1	316.2	356.8	702.2	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155S2B550C4-425AXSP04	231.4	376.5	282.1	320.5	-	234.6	377	283.9	322	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550C4-432AXSP04	214.1	350.5	261.7	298.1	-	216.8	351.2	263.3	298.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155S2B550C4-525AXSP04	254.2	409	308.3	349.3	-	258	410	310.3	350.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155S2B550C4-532AXSP04	238.6	387.9	291.2	330.1	-	242.1	388.2	293.1	331.4	-	3								

EAW-FD155SZB550K4-625AXSP04	260.1	415.9	315.7	356	698.8	264	416.2	317.1	356.8	693.7	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB550K4-632AXSP06	266.6	415.7	317.3	356.9	-	267.2	413.9	316.9	355.6	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155SZB550K5-425AXSP04	221.8	360.6	270.4	306.8	-	224.8	361.3	271.9	307.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550K5-432AXSP04	205.5	336.1	251.2	285.7	-	208.2	336.6	252.5	286.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550K5-525AXSP04	244	392.8	296.2	335.3	-	247.4	393.4	297.8	336.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550K8-532AXSP04	228.5	371.7	279.5	316.7	-	231.9	372	281	317.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550K5-625AXSP04	260.1	415.9	315.7	356	698.8	264	416.2	317.1	356.8	693.7	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB550K5-632AXSP06	266.6	415.7	317.3	356.9	-	267.2	413.9	316.9	355.6	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155SZB550K8-425AXSP04	221.8	360.6	270.4	306.8	-	224.8	361.3	271.9	307.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550K8-432AXSP04	205.5	336.1	251.2	285.7	-	208.2	336.6	252.5	286.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550K8-525AXSP04	244	392.8	296.2	335.3	-	247.4	393.4	297.8	336.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550K8-532AXSP04	228.5	371.7	279.5	316.7	-	231.9	372	281	317.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550K8-625AXSP04	260.1	415.9	315.7	356	698.8	264	416.2	317.1	356.8	693.7	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB550K8-632AXSP06	266.6	415.7	317.3	356.9	-	267.2	413.9	316.9	355.6	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155SZB550K9-425AXSP04	221.8	360.6	270.4	306.8	-	224.8	361.3	271.9	307.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550K9-432AXSP04	205.5	336.1	251.2	285.7	-	208.2	336.6	252.5	286.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550K9-525AXSP04	244	392.8	296.2	335.3	-	247.4	393.4	297.8	336.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550K9-532AXSP04	228.5	371.7	279.5	316.7	-	231.9	372	281	317.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550K9-625AXSP04	260.1	415.9	315.7	356	698.8	264	416.2	317.1	356.8	693.7	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB550K9-632AXSP06	266.6	415.7	317.3	356.9	-	267.2	413.9	316.9	355.6	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155SZB550R3-425AXSP04	226.1	367.7	275.4	313.2	-	229	367.9	277.1	313.8	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550R3-432AXSP04	209.3	342.6	255.9	291.3	-	212.1	342.9	257.5	292	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB550R3-525AXSP04	248.8	400.4	301.6	341.5	-	252.5	400.5	303.5	342.7	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550R3-532AXSP04	232.9	378.8	284.5	322.6	-	236.3	379.3	286.2	323.5	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB550R3-625AXSP04	265.3	423.9	321.6	362.8	711.8	269	424.4	323.2	363.7	707.8	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB550R3-632AXSP06	271.2	423.4	323.5	363.3	-	272.2	421.9	322.9	362.4	-	304	26.1	4"	244	20.4	3"	365	36.7	4"
EAW-FD155SZB750K2-425AXSP04	233.8	380.9	285.3	324.2	-	237.2	381.6	287.1	325.7	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K2-432AXSP04	216.6	354.7	264.9	301.8	-	219.6	355.8	266.9	302.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K2-525AXSP04	257.1	414	311.9	353.4	-	261.1	415.1	314	354.8	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K2-532AXSP04	241.4	392.4	294.4	334.4	-	244.9	392.7	296.3	335.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K2-625AXSP04	273.8	437.6	331.6	374.2	735.6	278	438.1	333.7	375.7	732.4	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K2-632AXSP04	260.7	421.4	318	359.9	715.2	264.9	422.2	319.9	361	711	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K3-425AXSP04	233.8	380.9	285.3	324.2	-	237.2	381.6	287.1	325.7	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K3-432AXSP04	216.6	354.7	264.9	301.8	-	219.6	355.8	266.9	302.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K3-525AXSP04	257.1	414	311.9	353.4	-	261.1	415.1	314	354.8	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K3-532AXSP04	241.4	392.4	294.4	334.4	-	244.9	392.7	296.3	335.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K3-625AXSP04	273.8	437.6	331.6	374.2	735.6	278	438.1	333.7	375.7	732.4	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K3-632AXSP04	260.7	421.4	318	359.9	715.2	264.9	422.2	319.9	361	711	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K4-425AXSP04	233.8	380.9	285.3	324.2	-	237.2	381.6	287.1	325.7	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K4-432AXSP04	216.6	354.7	264.9	301.8	-	219.6	355.8	266.9	302.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K4-525AXSP04	257.1	414	311.9	353.4	-	261.1	415.1	314	354.8	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K4-532AXSP04	241.4	392.4	294.4	334.4	-	244.9	392.7	296.3	335.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K4-625AXSP04	273.8	437.6	331.6	374.2	735.6	278	438.1	333.7	375.7	732.4	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K4-632AXSP04	260.7	421.4	318	359.9	715.2	264.9	422.2	319.9	361	711	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K5-425AXSP04	233.8	380.9	285.3	324.2	-	237.2	381.6	287.1	325.7	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K5-432AXSP04	216.6	354.7	264.9	301.8	-	219.6	355.8	266.9	302.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K5-525AXSP04	257.1	414	311.9	353.4	-	261.1	415.1	314	354.8	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K5-532AXSP04	241.4	392.4	294.4	334.4	-	244.9	392.7	296.3	335.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K5-625AXSP04	273.8	437.6	331.6	374.2	735.6	278	438.1	333.7	375.7	732.4	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K5-632AXSP04	260.7	421.4	318	359.9	715.2	264.9	422.2	319.9	361	711	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K8-425AXSP04	233.8	380.9	285.3	324.2	-	237.2	381.6	287.1	325.7	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K8-432AXSP04	216.6	354.7	264.9	301.8	-	219.6	355.8	266.9	302.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K8-525AXSP04	257.1	414	311.9	353.4	-	261.1	415.1	314	354.8	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K8-532AXSP04	241.4	392.4	294.4	334.4	-	244.9	392.7	296.3	335.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K8-625AXSP04	273.8	437.6	331.6	374.2	735.6	278	438.1	333.7	375.7	732.4	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K8-632AXSP04	260.7	421.4	318	359.9	715.2	264.9	422.2	319.9	361	711	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K9-425AXSP04	233.8	380.9	285.3	324.2	-	237.2	381.6	287.1	325.7	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K9-432AXSP04	216.6	354.7	264.9	301.8	-	219.6	355.8	266.9	302.6	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750K9-525AXSP04	257.1	414	311.9	353.4	-	261.1	415.1	314	354.8	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K9-532AXSP04	241.4	392.4	294.4	334.4	-	244.9	392.7	296.3	335.2	-	378	19.4	4"	302	12.8	4"	453	23.5	(2) 4"
EAW-FD155SZB750K9-625AXSP04	273.8	437.6	331.6	374.2	735.6	278	438.1	333.7	375.7	732.4	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750K9-632AXSP04	260.7	421.4	318	359.9	715.2	264.9	422.2	319.9	361	711	456	17.2	(2) 4"	365	13.8	4"	548	24.1	(2) 4"
EAW-FD155SZB750R3-425AXSP04	229.3	372.9	279.6	317.9	-	232.5	374.1	281.6	318.9	-	304	18.2	4"	244	15.1	3"	365	25.5	4"
EAW-FD155SZB750R3-432AXSP04	212.5	348	260	296	-	215.6	348.6	261.5	297	-</									

EAW-FD155SZK370K4-532AXSP04	228.7	367.6	277.6	314.1	623	230.9	366.4	277.8	313.5	617	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK370K4-625AXSP04	260.2	410.6	313.5	352.2	682.5	262.9	408.9	313.6	351.6	676.1	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK370K4-632AXSP04	247.5	395.4	300	338.8	663	250.1	393.8	300.4	337.9	656.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK370K5-425AXSP04	221.4	355.3	267.8	303.1	-	223.3	354.4	268.3	302.8	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK370K5-432AXSP04	205.1	331.5	249.2	282.6	-	206.9	330.5	249.6	282.6	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK370K5-525AXSP04	243.6	386.8	293.7	331.4	-	246	386.1	294.2	330.7	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK370K5-532AXSP04	228.7	367.6	277.6	314.1	623	230.9	366.4	277.8	313.5	617	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK370K5-625AXSP04	260.2	410.6	313.5	352.2	682.5	262.9	408.9	313.6	351.6	676.1	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK370K5-632AXSP04	247.5	395.4	300	338.8	663	250.1	393.8	300.4	337.9	656.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK370K8-425AXSP04	221.4	355.3	267.8	303.1	-	223.3	354.4	268.3	302.8	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK370K8-432AXSP04	205.1	331.5	249.2	282.6	-	206.9	330.5	249.6	282.6	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK370K8-525AXSP04	243.6	386.8	293.7	331.4	-	246	386.1	294.2	330.7	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK370K8-532AXSP04	228.7	367.6	277.6	314.1	623	230.9	366.4	277.8	313.5	617	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK370K8-625AXSP04	260.2	410.6	313.5	352.2	682.5	262.9	408.9	313.6	351.6	676.1	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK370K8-632AXSP04	247.5	395.4	300	338.8	663	250.1	393.8	300.4	337.9	656.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400B3-425AXSP04	221.1	354.8	267.9	303.3	-	223.5	354.7	268.5	303.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400B3-432AXSP04	205.8	332.8	250	283.6	-	207.8	332.2	250.8	283.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400B3-525AXSP04	241.6	384	291.2	328.6	-	244.1	383.6	292	328.7	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400B3-532AXSP04	228.2	366.1	277	312.8	621.4	230.4	365.7	277.3	312.9	615.7	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400B3-625AXSP04	255.6	402.9	307.7	345.7	669.3	258.6	402.6	308.4	346.2	664.5	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400B3-632AXSP06	262.3	405.2	310.6	348.5	-	262.7	402.7	310	346.7	-	304	28.6	4"	244	22	3"	365	40.1	4"
EAW-FD155SZK400C3-425AXSP04	228.6	367.1	276.7	313.5	-	230.4	366.7	277.6	313.6	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400C3-432AXSP04	211.9	342.8	257.7	292.2	-	213.8	342.3	258.2	292.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400C3-525AXSP04	251.3	398.9	302.5	341.6	-	253.7	398.3	303.1	341.4	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400C3-532AXSP04	236.1	379	286.3	324.1	-	238.9	378.6	287.1	323.6	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400C3-625AXSP04	266.7	420.6	320.8	361.1	700.5	269.7	420	321.8	360.9	694.9	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400C3-632AXSP04	255	406.7	309.2	348.8	683.7	257.7	406.3	309.6	348.4	678.2	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400C9-425AXSP04	228.6	367.1	276.7	313.5	-	230.4	366.7	277.6	313.6	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400C9-432AXSP04	211.9	342.8	257.7	292.2	-	213.8	342.3	258.2	292.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400C9-525AXSP04	251.3	398.9	302.5	341.6	-	253.7	398.3	303.1	341.4	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400C9-532AXSP04	236.1	379	286.3	324.1	-	238.9	378.6	287.1	323.6	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400C9-625AXSP04	266.7	420.6	320.8	361.1	700.5	269.7	420	321.8	360.9	694.9	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400C9-632AXSP04	255	406.7	309.2	348.8	683.7	257.7	406.3	309.6	348.4	678.2	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400K3-425AXSP04	221.4	355.3	267.8	303.1	-	223.3	354.4	268.3	302.8	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400K3-432AXSP04	205.1	331.5	249.2	282.6	-	206.9	330.5	249.6	282.6	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400K3-525AXSP04	243.6	386.8	293.7	331.4	-	246	386.1	294.2	330.7	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400K3-532AXSP04	228.7	367.6	277.6	314.1	623	230.9	366.4	277.8	313.5	617	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400K3-625AXSP04	260.2	410.6	313.5	352.2	682.5	262.9	408.9	313.6	351.6	676.1	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400K3-632AXSP04	247.5	395.4	300	338.8	663	250.1	393.8	300.4	337.9	656.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400K9-425AXSP04	221.4	355.3	267.8	303.1	-	223.3	354.4	268.3	302.8	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400K9-432AXSP04	205.1	331.5	249.2	282.6	-	206.9	330.5	249.6	282.6	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400K9-525AXSP04	243.6	386.8	293.7	331.4	-	246	386.1	294.2	330.7	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400K9-532AXSP04	228.7	367.6	277.6	314.1	623	230.9	366.4	277.8	313.5	617	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400K9-625AXSP04	260.2	410.6	313.5	352.2	682.5	262.9	408.9	313.6	351.6	676.1	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400K9-632AXSP04	247.5	395.4	300	338.8	663	250.1	393.8	300.4	337.9	656.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400R3-425AXSP04	224.2	360.4	271.5	307.4	-	226	359.2	272.2	307.3	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400R3-432AXSP04	207.8	335.9	252.5	286.4	-	209.7	335.7	253	286.2	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK400R3-525AXSP04	247	391.7	297.2	335.6	-	249	391.2	298	335	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400R3-532AXSP04	232	371.8	281.1	318.2	-	234	371	281.6	317.3	625.2	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK400R3-625AXSP04	263.5	415.4	317	356.7	690.7	265.9	414.4	317.3	355.7	684.5	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK400R3-632AXSP04	250.8	400.2	304.1	342.9	671.5	253.2	398.9	304.1	342.1	665.3	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK50B3-425AXSP04	238.7	383.9	289.2	328	-	241.1	384.5	290.4	328.3	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK50B3-432AXSP04	221.9	359.7	269.9	306.4	-	224.2	359.2	270.7	306.4	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK50B3-525AXSP04	261	415.5	314.5	355.4	-	263.8	415.1	315.9	355.5	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK50B3-532AXSP04	246.7	395.8	298.8	338	-	249.3	395.6	299.9	338.3	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK50B3-625AXSP04	276.3	435.9	332.1	374	726.6	279.7	435.6	333.4	374.6	721.5	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK50B3-632AXSP04	265.2	423.2	320.8	362.1	711.4	268.4	422.8	322.1	362.7	706.6	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK550C2-425AXSP04	253	408.1	306.9	348	-	255.5	407.8	308	348.2	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK550C2-432AXSP04	233.8	379.6	284.5	323.2	-	236.1	379.1	285.2	323.2	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZK550C2-525AXSP04	279.2	445	336.9	380.6	-	282.1	445	338.2	381	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK550C2-532AXSP04	262	421	317.4	359.5	-	264.6	421	318.2	359.4	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZK550C2-625AXSP04	299.4	471.3	359.2	404.3	-	302.5	471.3	360.3	404.6	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZK550C2-632AXSP04	284.7	453.9	343.6	388.3	-	287.8	453.6	344.6	388.5	759.9	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"

EAW-FD155SZ5K0K3-525AXSP04	267.1	425.2	322	364	-	269.8	425.2	322.7	363.9	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K3-532AXSP04	251.1	402.5	303.6	344.2	-	253.2	402.2	304.7	343.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K3-625AXSP04	286.7	451.7	344.2	387.2	753.7	289.3	450.5	344.9	387.2	747.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K3-632AXSP04	272.2	433.7	328.9	371.4	730.7	274.8	433.4	329.9	371	724.8	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K4-425AXSP04	242.2	390	293.7	333	-	244.6	390	294.3	332.9	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K4-432AXSP04	224.2	363.2	272.7	309.4	-	226.1	363	273.2	309.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K4-525AXSP04	267.1	425.2	322	364	-	269.8	425.2	322.7	363.9	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K4-532AXSP04	251.1	402.5	303.6	344.2	-	253.2	402.2	304.7	343.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K4-625AXSP04	286.7	451.7	344.2	387.2	753.7	289.3	450.5	344.9	387.2	747.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K4-632AXSP04	272.2	433.7	328.9	371.4	730.7	274.8	433.4	329.9	371	724.8	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K5-425AXSP04	242.2	390	293.7	333	-	244.6	390	294.3	332.9	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K5-432AXSP04	224.2	363.2	272.7	309.4	-	226.1	363	273.2	309.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K5-525AXSP04	267.1	425.2	322	364	-	269.8	425.2	322.7	363.9	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K5-532AXSP04	251.1	402.5	303.6	344.2	-	253.2	402.2	304.7	343.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K5-625AXSP04	286.7	451.7	344.2	387.2	753.7	289.3	450.5	344.9	387.2	747.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K5-632AXSP04	272.2	433.7	328.9	371.4	730.7	274.8	433.4	329.9	371	724.8	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K8-425AXSP04	242.2	390	293.7	333	-	244.6	390	294.3	332.9	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K8-432AXSP04	224.2	363.2	272.7	309.4	-	226.1	363	273.2	309.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K8-525AXSP04	267.1	425.2	322	364	-	269.8	425.2	322.7	363.9	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K8-532AXSP04	251.1	402.5	303.6	344.2	-	253.2	402.2	304.7	343.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K8-625AXSP04	286.7	451.7	344.2	387.2	753.7	289.3	450.5	344.9	387.2	747.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K8-632AXSP04	272.2	433.7	328.9	371.4	730.7	274.8	433.4	329.9	371	724.8	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K9-432AXSP04	224.2	363.2	272.7	309.4	-	226.1	363	273.2	309.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0K9-525AXSP04	267.1	425.2	322	364	-	269.8	425.2	322.7	363.9	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K9-532AXSP04	251.1	402.5	303.6	344.2	-	253.2	402.2	304.7	343.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0K9-625AXSP04	286.7	451.7	344.2	387.2	753.7	289.3	450.5	344.9	387.2	747.7	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0K9-632AXSP04	272.2	433.7	328.9	371.4	730.7	274.8	433.4	329.9	371	724.8	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0R3-425AXSP04	247	398.4	299.7	339.9	-	249.6	398	300.6	340.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0R3-432AXSP04	228.6	370.7	278	315.9	-	230.8	370.3	278.9	315.9	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ5K0R3-525AXSP04	272.3	434	328.4	371.5	-	275.3	433.6	329.4	371.5	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0R3-532AXSP04	256	410.8	309.6	350.5	-	258.2	410.1	310.9	350.9	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ5K0R3-625AXSP04	292.6	460.8	350.9	395.5	-	295.5	459.9	351.9	395	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0R3-632AXSP04	277.4	442.5	335.3	378.7	746.1	280.6	441.7	336.5	378.5	739.4	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ5K0C4-425AXSP04	264.1	426.3	320.4	363.5	-	266.7	426.8	321.9	363.9	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750C4-432AXSP04	244.2	396.8	297.5	338	-	246.9	397.3	298.7	338.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750C4-525AXSP04	289.9	463.3	350.1	395.8	-	293.6	463.6	351.7	397.2	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750C4-532AXSP04	272.8	438.9	330.8	374.4	-	275.8	439.2	331.8	375.1	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750C4-632AXSP04	295.5	471.6	357	403	-	299.4	471.5	358.2	404.1	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750C5-425AXSP04	264.1	426.3	320.4	363.5	-	266.7	426.8	321.9	363.9	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750C5-432AXSP04	244.2	396.8	297.5	338	-	246.9	397.3	298.7	338.5	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750C5-525AXSP04	289.9	463.3	350.1	395.8	-	293.6	463.6	351.7	397.2	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750C5-532AXSP04	272.8	438.9	330.8	374.4	-	275.8	439.2	331.8	375.1	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750C5-632AXSP04	295.5	471.6	357	403	-	299.4	471.5	358.2	404.1	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K2-425AXSP04	256.3	413.6	311.4	353.2	-	259.2	413.7	312.6	353.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K2-432AXSP04	237.4	385.5	289	328.4	-	239.7	385.4	290.1	328.4	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K2-525AXSP04	282.5	450.6	341	385.3	-	285.5	450.7	342.4	385.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750K2-532AXSP04	265.2	426.6	321.4	364.2	-	268.1	426.4	322.6	364.5	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750K2-625AXSP04	303.1	477.4	363.6	409.4	-	306.3	477.5	364.9	409.9	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K2-632AXSP04	287.9	459.5	347.7	393	-	291.2	458.6	348.8	393.2	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K3-425AXSP04	256.3	413.6	311.4	353.2	-	259.2	413.7	312.6	353.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K3-432AXSP04	237.4	385.5	289	328.4	-	239.7	385.4	290.1	328.4	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K3-525AXSP04	282.5	450.6	341	385.3	-	285.5	450.7	342.4	385.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750K3-532AXSP04	265.2	426.6	321.4	364.2	-	268.1	426.4	322.6	364.5	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750K3-625AXSP04	303.1	477.4	363.6	409.4	-	306.3	477.5	364.9	409.9	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K3-632AXSP04	287.9	459.5	347.7	393	-	291.2	458.6	348.8	393.2	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K4-425AXSP04	256.3	413.6	311.4	353.2	-	259.2	413.7	312.6	353.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K4-432AXSP04	237.4	385.5	289	328.4	-	239.7	385.4	290.1	328.4	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K4-525AXSP04	282.5	450.6	341	385.3	-	285.5	450.7	342.4	385.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750K4-532AXSP04	265.2	426.6	321.4	364.2	-	268.1	426.4	322.6	364.5	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW-FD155SZ750K4-625AXSP04	303.1	477.4	363.6	409.4	-	306.3	477.5	364.9	409.9	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K4-632AXSP04	287.9	459.5	347.7	393	-	291.2	458.6	348.8	393.2	-	456	18.8	(2) 4"	365	14.9	4"	548	26.4	(2) 4"
EAW-FD155SZ750K5-425AXSP04	256.3	413.6	311.4	353.2	-	259.2	413.7	312.6	353.1	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K5-432AXSP04	237.4	385.5	289	328.4	-	239.7	385.4	290.1	328.4	-	304	19.8	4"	244	16.2	3"	365	27.8	4"
EAW-FD155SZ750K5-525AXSP04	282.5	450.6	341	385.3	-	285.5	450.7	342.4	385.8	-	378	21.1	4"	302	13.9	4"	453	25.8	(2) 4"
EAW																			

EAW-FD1556PB400C9-532AXSP04	246.7	394.2	297.6	336.7	-	249.1	393.8	299.1	337.4	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400C9-625AXSP04	274.3	428.7	327.6	367.8	-	277.4	429.3	329.1	368.7	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400C9-632AXSP04	264.5	417.8	317.2	358	-	267.1	417.4	318.5	358	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400K3-425AXSP04	232.8	373	281.2	318.7	-	234.8	372.6	282.1	318.3	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB400K3-432AXSP04	216.1	348.4	262.1	297.2	-	218	347.8	262.6	297.1	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB400K3-525AXSP04	256.9	406.3	308.8	348.3	-	259.2	406.1	309.3	348	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400K3-532AXSP04	242	386.2	291.9	330	-	244.2	385.5	292.5	329.9	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400K3-625AXSP04	273.4	427.8	326.5	367.1	-	275.7	426.6	327.1	366.9	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400K3-632AXSP04	261.1	412.9	313.6	353.3	-	263.3	411.8	314.4	353.4	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400K9-425AXSP04	232.8	373	281.2	318.7	-	234.8	372.6	282.1	318.3	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB400K9-432AXSP04	216.1	348.4	262.1	297.2	-	218	347.8	262.6	297.1	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB400K9-525AXSP04	256.9	406.3	308.8	348.3	-	259.2	406.1	309.3	348	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400K9-532AXSP04	242	386.2	291.9	330	-	244.2	385.5	292.5	329.9	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400K9-625AXSP04	273.4	427.8	326.5	367.1	-	275.7	426.6	327.1	366.9	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400K9-632AXSP04	261.1	412.9	313.6	353.3	-	263.3	411.8	314.4	353.4	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400R3-425AXSP04	235.3	376.9	284.5	322	-	237.2	376.7	285.1	321.7	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB400R3-432AXSP04	218.5	352.2	265	300.6	-	220.2	351.8	265.7	300.3	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB400R3-525AXSP04	259.4	410.5	311.4	351.2	-	261.5	409.9	312.5	351.6	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400R3-532AXSP04	244.7	390	295.2	333.8	-	246.5	389.5	295.9	333.2	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB400R3-625AXSP04	275.8	431.2	329.4	370.4	-	278.3	430.8	330.2	370.4	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB400R3-632AXSP04	263.6	416.3	316.6	356.7	-	265.9	416.1	317	356.9	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550B3-425AXSP02	189.1	352.6	250.9	293.8	629.2	201.7	358.6	259	300.2	630.1	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550B3-432AXSP04	229.3	370.3	278.3	315.7	-	231.9	371	279.8	316.3	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB550B3-525AXSP02	-	-	-	-	-	-	-	-	-	-	676	12.2	(2) 4"	541	8	(2) 4"	812	17.2	(2) 4"
EAW-FD1556PB550B3-532AXSP04	-	-	-	-	-	257	406.5	308.3	347.9	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.7	(3) 4"
EAW-FD1556PB550B3-632AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.7	(3) 4"
EAW-FD1556PB550C3-425AXSP02	204.2	378.1	270	315.8	676	216.9	383.9	278	322.3	676.4	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550C3-432AXSP02	186.8	351.6	248.9	292.2	632.7	199.2	357.3	256.7	298.3	632.9	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550C3-525AXSP04	288.5	458.2	347	392.2	-	291.6	458.7	348.6	393	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550C3-532AXSP04	271.9	435.3	328.7	371.9	-	274.9	436.3	330.3	372.6	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550C3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.7	(3) 4"
EAW-FD1556PB550C3-632AXSP04	-	-	-	-	-	295.6	464	353.1	397.6	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550C9-425AXSP02	204.2	378.1	270	315.8	676	216.9	383.9	278	322.3	676.4	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550C9-432AXSP02	186.8	351.6	248.9	292.2	632.7	199.2	357.3	256.7	298.3	632.9	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550C9-525AXSP04	288.5	458.2	347	392.2	-	291.6	458.7	348.6	393	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550C9-532AXSP04	271.9	435.3	328.7	371.9	-	274.9	436.3	330.3	372.6	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550C9-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.7	(3) 4"
EAW-FD1556PB550C9-632AXSP04	-	-	-	-	-	295.6	464	353.1	397.6	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550K3-425AXSP02	195.8	363.9	259	303.2	649.8	208	369	266.5	309.2	649.7	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550K3-432AXSP04	234.2	378.5	284.4	322.8	-	236.5	378.7	285.2	323	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB550K3-432AXSP04	278.8	442.6	335.8	378.6	-	281.6	442.6	336.4	379	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550K3-532AXSP04	262.5	419.7	317	359.1	-	264.7	419.7	318.3	358.9	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550K3-625AXSP04	297	466	355.1	399.7	-	299.7	465.5	356.4	399.7	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550K3-632AXSP04	283.2	448.6	340.6	384.3	-	285.7	448.3	341.6	384.4	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550K9-425AXSP02	195.8	363.9	259	303.2	649.8	208	369	266.5	309.2	649.7	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550K9-432AXSP04	234.2	378.5	284.4	322.8	-	236.5	378.7	285.2	323	-	270	20.6	4"	216	16	3"	325	28.9	4"
EAW-FD1556PB550K9-525AXSP04	278.8	442.6	335.8	378.6	-	281.6	442.6	336.4	379	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550K9-532AXSP04	262.5	419.7	317	359.1	-	264.7	419.7	318.3	358.9	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550K9-625AXSP04	297	466	355.1	399.7	-	299.7	465.5	356.4	399.7	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550K9-632AXSP04	283.2	448.6	340.6	384.3	-	285.7	448.3	341.6	384.4	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550R3-425AXSP02	199.5	370.1	264.2	309.1	661.8	211.9	375.3	271.7	315.1	660.9	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550R3-432AXSP02	182.2	343.6	243.4	285.9	619.4	194.3	348.7	250.7	291.5	619.2	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB550R3-525AXSP04	283.7	450.1	341.1	385.4	-	286.1	450.3	342.6	386	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550R3-532AXSP04	267	427.4	322.5	364.8	-	269.5	427.2	323.7	365.1	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB550R3-625AXSP04	302	473.6	361.2	406.7	-	304.9	474	362.1	406.8	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB550R3-632AXSP04	287.9	455.8	346.4	390.3	-	290.6	455.7	347	390.6	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB750K3-425AXSP02	206.9	382.1	273	319.4	683.9	219.5	388.2	281.2	326.1	684.6	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB750K3-432AXSP02	189.1	355.4	251.7	295.6	639.6	201.4	361.3	259.7	301.9	639.9	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB750K3-525AXSP04	291.7	463.8	351.6	396.8	-	295.2	464.6	353	398	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB750K3-532AXSP04	275	440.1	332.1	375.9	-	277.7	440.5	333.8	376.7	-	338	21.6	4"	270	14.3	4"	406	30.4	4"
EAW-FD1556PB750K3-625AXSP04	310.3	487.3	371.2	418.1	-	313.1	487.6	372.7	418.8	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB750K3-632AXSP04	296.1	469.7	355.9	401.9	-	299.4	469.4	357.6	402.7	-	406	22.9	4"	325	15.1	4"	487	27.8	(2) 4"
EAW-FD1556PB750K9-425AXSP02	206.9	382.1	273	319.4	683.9	219.5	388.2	281.2	326.1	684.6	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB750K9-432AXSP02	189.1	355.4	251.7	295.6	639.6	201.4	361.3	259.7	301.9	639.9	541	11.2	(2) 4"	433	10.8	4"	649	15.7	(2) 4"
EAW-FD1556PB750K9-525AXSP04	291.7																		

EAW-FD1556ZB370K2-525AXSP04	276.8	437.7	332.6	374.9	-	278.8	436.8	333.1	374.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K2-532AXSP04	260.8	415.3	314.3	355.2	-	262.7	414.6	314.6	354.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K2-625AXSP04	296.8	463	354.3	398.1	-	298.9	461.8	354.4	397.4	762.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K2-632AXSP04	282.8	446.2	339.9	382.7	747.9	284.6	444.9	340.2	382.1	741.5	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K4-425AXSP04	251.7	402.3	304	343.6	-	253.3	401.4	304.5	343.3	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB370K4-432AXSP04	233.6	376.3	283	320.8	-	235.1	375	283.2	320.1	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB370K4-525AXSP04	276.8	437.7	332.6	374.9	-	278.8	436.8	333.1	374.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K4-532AXSP04	260.8	415.3	314.3	355.2	-	262.7	414.6	314.6	354.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K4-625AXSP04	296.8	463	354.3	398.1	-	298.9	461.8	354.4	397.4	762.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K4-632AXSP04	282.8	446.2	339.9	382.7	747.9	284.6	444.9	340.2	382.1	741.5	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K5-425AXSP04	251.7	402.3	304	343.6	-	253.3	401.4	304.5	343.3	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB370K5-432AXSP04	233.6	376.3	283	320.8	-	235.1	375	283.2	320.1	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB370K5-525AXSP04	276.8	437.7	332.6	374.9	-	278.8	436.8	333.1	374.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K5-532AXSP04	260.8	415.3	314.3	355.2	-	262.7	414.6	314.6	354.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K5-625AXSP04	296.8	463	354.3	398.1	-	298.9	461.8	354.4	397.4	762.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K5-632AXSP04	282.8	446.2	339.9	382.7	747.9	284.6	444.9	340.2	382.1	741.5	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K8-425AXSP04	251.7	402.3	304	343.6	-	253.3	401.4	304.5	343.3	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB370K8-432AXSP04	233.6	376.3	283	320.8	-	235.1	375	283.2	320.1	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB370K8-525AXSP04	276.8	437.7	332.6	374.9	-	278.8	436.8	333.1	374.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K8-532AXSP04	260.8	415.3	314.3	355.2	-	262.7	414.6	314.6	354.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB370K8-625AXSP04	296.8	463	354.3	398.1	-	298.9	461.8	354.4	397.4	762.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB370K8-632AXSP04	282.8	446.2	339.9	382.7	747.9	284.6	444.9	340.2	382.1	741.5	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400B3-425AXSP04	250.1	399.9	301.7	341.7	-	252.5	399.9	302.9	341.4	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400B3-432AXSP04	233.1	375.4	282.6	320.4	-	235	374.8	283.1	320.3	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400B3-525AXSP04	272.5	429.8	326.8	368.3	-	274.9	429.7	327.8	368.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400B3-532AXSP04	258.5	412	311.4	351.9	-	261	411.1	312.5	352.1	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	913	11.7	(3) 4"	730	9.6	(2) 4"	1096	16.5	(3) 4"
EAW-FD1556ZB400B3-632AXSP04	277.6	438.3	333.7	375.6	734.2	280.3	437.8	334.4	376.1	729.3	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400C3-425AXSP04	258.7	414	312.9	354	-	260.9	413.8	313.4	353.5	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400C3-432AXSP04	240.7	387.5	291.8	330.7	-	242.6	387.4	292.1	330.4	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400C3-525AXSP04	283.4	448	340.1	383.5	-	285.7	447.6	340.9	383.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400C3-532AXSP04	267.8	427.1	322.9	365	-	270.2	426.5	323.7	364.9	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400C3-625AXSP04	300.9	470.4	359.2	403.7	-	304	470	360.6	404.4	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400C3-632AXSP04	289	456.6	347	391.5	-	291.7	455.8	348.2	391.2	760.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400C9-425AXSP04	258.7	414	312.9	354	-	260.9	413.8	313.4	353.5	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400C9-432AXSP04	240.7	387.5	291.8	330.7	-	242.6	387.4	292.1	330.4	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400C9-525AXSP04	283.4	448	340.1	383.5	-	285.7	447.6	340.9	383.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400C9-532AXSP04	267.8	427.1	322.9	365	-	270.2	426.5	323.7	364.9	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400C9-625AXSP04	300.9	470.4	359.2	403.7	-	304	470	360.6	404.4	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400C9-632AXSP04	289	456.6	347	391.5	-	291.7	455.8	348.2	391.2	760.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400K3-425AXSP04	251.7	402.3	304	343.6	-	253.3	401.4	304.5	343.3	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400K3-432AXSP04	233.6	376.3	283	320.8	-	235.1	375	283.2	320.1	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400K3-525AXSP04	276.8	437.7	332.6	374.9	-	278.8	436.8	333.1	374.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400K3-532AXSP04	260.8	415.3	314.3	355.2	-	262.7	414.6	314.6	354.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400K3-625AXSP04	296.8	463	354.3	398.1	-	298.9	461.8	354.4	397.4	762.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400K3-632AXSP04	282.8	446.2	339.9	382.7	747.9	284.6	444.9	340.2	382.1	741.5	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400K9-425AXSP04	251.7	402.3	304	343.6	-	253.3	401.4	304.5	343.3	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400K9-432AXSP04	233.6	376.3	283	320.8	-	235.1	375	283.2	320.1	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400K9-525AXSP04	276.8	437.7	332.6	374.9	-	278.8	436.8	333.1	374.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400K9-532AXSP04	260.8	415.3	314.3	355.2	-	262.7	414.6	314.6	354.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400K9-625AXSP04	296.8	463	354.3	398.1	-	298.9	461.8	354.4	397.4	762.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400K9-632AXSP04	282.8	446.2	339.9	382.7	747.9	284.6	444.9	340.2	382.1	741.5	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400R3-425AXSP04	254.6	407.3	307.5	347.7	-	256.3	406.5	308.3	347.6	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400R3-432AXSP04	236.4	380.5	286.5	324.5	-	238.2	380.2	287	324.4	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB400R3-525AXSP04	280.2	442.6	336.1	379	-	281.9	441.8	336.8	378.7	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400R3-532AXSP04	263.7	420.1	317.8	359.2	-	265.7	419	318.2	358.7	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB400R3-625AXSP04	299.4	468	357.5	401.8	-	302.1	467	357.8	401.3	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB400R3-632AXSP04	285.6	451.7	343.4	386.8	756.3	288.1	449.9	343.8	386.3	750.2	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD1556ZB550B3-425AXSP04	268.7	430.9	324.9	367.9	-	271.5	430.9	326.4	368.4	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB550B3-432AXSP04	250.4	404.1	303.6	344.5	-	252.8	404	304.8	344.7	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD1556ZB550B3-525AXSP04	292.7	463	351.5	396.6	-	295.4	463.5	353.2	397.5	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB550B3-532AXSP04	277.3	442.7	334.6	378.6	-	284.1	443.3	335.9	379	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD1556ZB550B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	913	11.7	(3) 4"	730	9.6	(2) 4"	1096	16.5	(3) 4"
EAW-FD1556ZB550B3-632AXSP04	-	-	-	-	-	301.4	471.9	359.4	404.7	-	456	20.1	(2) 4"</						

EAW-FD11556ZB550K2-432AXSP04	254	410.4	308.4	349.7	-	256.4	409.8	309.2	349.8	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD11556ZB550K2-525AXSP04	302.1	478.8	363.6	409.8	-	304.4	478.6	364.2	410.1	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K2-532AXSP04	283.9	453.9	342.7	387.9	-	286	453.3	343.7	387.2	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K2-625AXSP04	323.9	507.4	387.1	435.5	-	326.4	506.4	388.1	435	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD11556ZB550K2-632AXSP04	308.5	488.5	370.8	418.1	-	311.1	487.2	371.2	417.5	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD11556ZB550K3-425AXSP02	211.2	393.8	280.1	328.2	703.1	224.7	399.1	288.4	334.2	702	609	11.7	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD11556ZB550K3-432AXSP04	254	410.4	308.4	349.7	-	256.4	409.8	309.2	349.8	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD11556ZB550K3-525AXSP04	302.1	478.8	363.6	409.8	-	304.4	478.6	364.2	410.1	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K3-532AXSP04	283.9	453.9	342.7	387.9	-	286	453.3	343.7	387.2	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K3-625AXSP04	323.9	507.4	387.1	435.5	-	326.4	506.4	388.1	435	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD11556ZB550K3-632AXSP04	308.5	488.5	370.8	418.1	-	311.1	487.2	371.2	417.5	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD11556ZB550K4-425AXSP02	211.2	393.8	280.1	328.2	703.1	224.7	399.1	288.4	334.2	702	609	11.7	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD11556ZB550K4-432AXSP04	254	410.4	308.4	349.7	-	256.4	409.8	309.2	349.8	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD11556ZB550K4-525AXSP04	302.1	478.8	363.6	409.8	-	304.4	478.6	364.2	410.1	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K4-532AXSP04	283.9	453.9	342.7	387.9	-	286	453.3	343.7	387.2	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K4-625AXSP04	323.9	507.4	387.1	435.5	-	326.4	506.4	388.1	435	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD11556ZB550K4-632AXSP04	308.5	488.5	370.8	418.1	-	311.1	487.2	371.2	417.5	-	456	20.1	(2) 4"	365	15.8	4"	548	28.2	(2) 4"
EAW-FD11556ZB550K5-425AXSP02	211.2	393.8	280.1	328.2	703.1	224.7	399.1	288.4	334.2	702	609	11.7	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD11556ZB550K5-432AXSP04	254	410.4	308.4	349.7	-	256.4	409.8	309.2	349.8	-	304	21.1	4"	244	17.1	3"	365	29.7	4"
EAW-FD11556ZB550K5-525AXSP04	302.1	478.8	363.6	409.8	-	304.4	478.6	364.2	410.1	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"
EAW-FD11556ZB550K5-532AXSP04	283.9	453.9	342.7	387.9	-	286	453.3	343.7	387.2	-	378	22.4	4"	302	14.7	4"	453	27.6	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1556ZK370C8-425AXSP02	225.6	405.9	292.7	339.9	714.3	236.4	409.2	298.8	344	711.4	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK370C8-432AXSP04	261.4	417.8	315.3	356.8	-	262.6	416.2	315.1	355.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370C8-525AXSP04	309.4	485.9	370.3	416.5	-	311.2	484.3	369.7	415.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370C8-532AXSP04	291.6	461.7	350.5	395.2	-	293.1	460.2	350.1	394.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370C8-625AXSP04	330	511.5	392.4	440.1	-	332	510	392.4	439.2	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370C8-632AXSP04	316.5	495.2	377.7	425.1	-	318	493.2	377.5	423.8	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370K2-425AXSP04	272.5	432.9	328.1	370.4	-	273.7	431.1	327.4	369.3	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370K2-432AXSP04	252.9	403.9	305.1	345	-	254	402.6	304.8	343.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370K2-525AXSP04	300.5	471.1	359.4	404	-	301.6	469.4	358.8	403.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370K2-532AXSP04	282.9	447.6	339.8	382.8	-	284.3	445.4	339.4	381.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370K2-625AXSP04	322.4	499.3	382.8	429.8	-	323.5	497.1	382.3	427.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370K2-632AXSP04	307.6	481.3	367	412.8	-	309.1	478.7	366.7	411.6	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370K4-425AXSP04	272.5	432.9	328.1	370.4	-	273.7	431.1	327.4	369.3	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370K4-432AXSP04	252.9	403.9	305.1	345	-	254	402.6	304.8	343.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370K4-525AXSP04	300.5	471.1	359.4	404	-	301.6	469.4	358.8	403.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370K4-532AXSP04	282.9	447.6	339.8	382.8	-	284.3	445.4	339.4	381.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370K4-625AXSP04	322.4	499.3	382.8	429.8	-	323.5	497.1	382.3	427.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370K4-632AXSP04	307.6	481.3	367	412.8	-	309.1	478.7	366.7	411.6	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370K5-425AXSP04	272.5	432.9	328.1	370.4	-	273.7	431.1	327.4	369.3	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370K5-432AXSP04	252.9	403.9	305.1	345	-	254	402.6	304.8	343.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK370K5-525AXSP04	300.5	471.1	359.4	404	-	301.6	469.4	358.8	403.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370K5-532AXSP04	282.9	447.6	339.8	382.8	-	284.3	445.4	339.4	381.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK370K5-625AXSP04	322.4	499.3	382.8	429.8	-	323.5	497.1	382.3	427.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK370K5-632AXSP04	307.6	481.3	367	412.8	-	309.1	478.7	366.7	411.6	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400B3-425AXSP04	272.7	432.4	327.7	369.9	-	273.9	431.4	327.6	368.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400B3-432AXSP04	253.7	405.4	306.1	346.3	-	254.9	403.8	305.9	345.5	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400B3-525AXSP04	298	467	356.3	401.2	-	299.8	465.7	356.6	399.9	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400B3-532AXSP04	282.3	445.8	338.4	382	-	283.7	444.5	338.7	381.3	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400B3-625AXSP04	316.5	489.9	376.3	421.8	-	318.7	488.7	376.5	421.2	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400B3-632AXSP04	304.8	476.7	364.1	408.9	-	306.5	475.2	364.2	408.1	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400C3-425AXSP02	225.6	405.9	292.7	339.9	714.3	236.4	409.2	298.8	344	711.4	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK400C3-432AXSP04	261.4	417.8	315.3	356.8	-	262.6	416.2	315.1	355.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400C3-525AXSP04	309.4	485.9	370.3	416.5	-	311.2	484.3	369.7	415.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400C3-532AXSP04	291.6	461.7	350.5	395.2	-	293.1	460.2	350.1	394.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400C3-625AXSP04	330	511.5	392.4	440.1	-	332	510	392.4	439.2	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400C3-632AXSP04	316.5	495.2	377.7	425.1	-	318	493.2	377.5	423.8	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400C9-425AXSP02	225.6	405.9	292.7	339.9	714.3	236.4	409.2	298.8	344	711.4	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK400C9-432AXSP04	261.4	417.8	315.3	356.8	-	262.6	416.2	315.1	355.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400C9-525AXSP04	309.4	485.9	370.3	416.5	-	311.2	484.3	369.7	415.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400C9-532AXSP04	291.6	461.7	350.5	395.2	-	293.1	460.2	350.1	394.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400C9-625AXSP04	330	511.5	392.4	440.1	-	332	510	392.4	439.2	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400C9-632AXSP04	316.5	495.2	377.7	425.1	-	318	493.2	377.5	423.8	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400K3-425AXSP04	272.5	432.9	328.1	370.4	-	273.7	431.1	327.4	369.3	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400K3-432AXSP04	252.9	403.9	305.1	345	-	254	402.6	304.8	343.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400K3-525AXSP04	300.5	471.1	359.4	404	-	301.6	469.4	358.8	403.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400K3-632AXSP04	282.9	447.6	339.8	382.8	-	284.3	445.4	339.4	381.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400K9-425AXSP04	322.4	499.3	382.8	429.8	-	323.5	497.1	382.3	427.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400K9-432AXSP04	307.6	481.3	367	412.8	-	309.1	478.7	366.7	411.6	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400K9-525AXSP04	272.5	432.9	328.1	370.4	-	273.7	431.1	327.4	369.3	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400K9-632AXSP04	252.9	403.9	305.1	345	-	254	402.6	304.8	343.9	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400K9-625AXSP04	300.5	471.1	359.4	404	-	301.6	469.4	358.8	403.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400K9-632AXSP04	282.9	447.6	339.8	382.8	-	284.3	445.4	339.4	381.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400K9-625AXSP04	322.4	499.3	382.8	429.8	-	323.5	497.1	382.3	427.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400K9-632AXSP04	307.6	481.3	367	412.8	-	309.1	478.7	366.7	411.6	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400R3-425AXSP02	220.8	397.4	286.6	333	699.8	231.5	401	292.6	337.5	697.5	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK400R3-432AXSP04	256.1	409.2	309.1	349.7	-	257.4	408.1	309.1	348.4	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK400R3-525AXSP04	304.1	477.1	363.8	409.1	-	305.4	475	363.4	407.6	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400R3-532AXSP04	286.4	452.8	344.1	387.8	-	287.6	451	343.4	386.7	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK400R3-625AXSP04	326	505.2	387.7	434.7	-	327.3	503.2	386.8	432.8	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK400R3-632AXSP04	311.3	487.3	372	417.8	-	312.4	484.8	371.3	416.8	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550B3-425AXSP02	236.8	423.7	306.4	355.9	748.1	248	428.3	313.4	361.1	745.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550B3-432AXSP02	217.5	395.8	283.7	330.9	702.3	228.7	399.7	290.5	335.5	701.5	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550B3-525AXSP04	321.6	505.5	385.1	433.5	-	323.7	504.9	385.4	433.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550B3-532AXSP04	304.3	482.2	365.4	412.2	-	306.1	481.1	365.9											



EAW-FD1556ZK550C8-632AXSP04	351.4	552.2	420.7	473.5	-	353.7	550.8	420.5	472.9	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550C9-425AXSP02	252.5	450.2	326.6	378.9	795.5	264	454.1	333.3	383.9	793.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550C9-432AXSP02	230.7	417.6	300.2	349.9	742.2	241.5	421.5	306.9	354.6	740.7	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550C9-525AXSP02	277.3	494.4	358.2	415.3	864.4	291.1	499.3	366.2	421.1	862	761	14	(2) 4"	609	9.2	(2) 4"	913	16.8	(3) 4"
EAW-FD1556ZK550C9-532AXSP04	322.9	513.1	388.3	438.6	-	324.5	511.2	388.3	438.3	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550C9-625AXSP04	368.6	574.3	439	493	-	370.9	572.5	439.6	492.6	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550C9-632AXSP04	351.4	552.2	420.7	473.5	-	353.7	550.8	420.5	472.9	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K2-425AXSP02	240.7	431	311.4	361.9	760.4	251.9	434.2	318	366.2	756.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K2-432AXSP02	220.1	400	286.8	334.3	711	230.8	403.8	293.3	338.8	707.8	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K2-525AXSP04	329.2	518.1	394.4	444	-	331.2	516.4	394.5	443.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K2-532AXSP04	309.1	490.4	372	419.8	-	310.9	489.1	371.8	418.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K2-625AXSP04	353.8	549.4	420.6	472.8	-	355.2	547.9	420.7	471.3	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K2-632AXSP04	336.4	528.2	402.6	452.8	-	338.2	526.2	402.4	451.5	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K3-425AXSP02	240.7	431	311.4	361.9	760.4	251.9	434.2	318	366.2	756.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K3-432AXSP02	220.1	400	286.8	334.3	711	230.8	403.8	293.3	338.8	707.8	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K3-525AXSP04	329.2	518.1	394.4	444	-	331.2	516.4	394.5	443.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K3-532AXSP04	309.1	490.4	372	419.8	-	310.9	489.1	371.8	418.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K3-625AXSP04	353.8	549.4	420.6	472.8	-	355.2	547.9	420.7	471.3	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K3-632AXSP04	336.4	528.2	402.6	452.8	-	338.2	526.2	402.4	451.5	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K4-425AXSP02	240.7	431	311.4	361.9	760.4	251.9	434.2	318	366.2	756.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K4-432AXSP02	220.1	400	286.8	334.3	711	230.8	403.8	293.3	338.8	707.8	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K4-525AXSP04	329.2	518.1	394.4	444	-	331.2	516.4	394.5	443.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K4-532AXSP04	309.1	490.4	372	419.8	-	310.9	489.1	371.8	418.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K4-625AXSP04	353.8	549.4	420.6	472.8	-	355.2	547.9	420.7	471.3	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K4-632AXSP04	336.4	528.2	402.6	452.8	-	338.2	526.2	402.4	451.5	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K8-425AXSP02	240.7	431	311.4	361.9	760.4	251.9	434.2	318	366.2	756.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K8-432AXSP02	220.1	400	286.8	334.3	711	230.8	403.8	293.3	338.8	707.8	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K8-525AXSP04	329.2	518.1	394.4	444	-	331.2	516.4	394.5	443.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K8-532AXSP04	309.1	490.4	372	419.8	-	310.9	489.1	371.8	418.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K8-625AXSP04	353.8	549.4	420.6	472.8	-	355.2	547.9	420.7	471.3	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K8-632AXSP04	336.4	528.2	402.6	452.8	-	338.2	526.2	402.4	451.5	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K9-425AXSP02	240.7	431	311.4	361.9	760.4	251.9	434.2	318	366.2	756.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K9-432AXSP02	220.1	400	286.8	334.3	711	230.8	403.8	293.3	338.8	707.8	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K9-525AXSP04	329.2	518.1	394.4	444	-	331.2	516.4	394.5	443.1	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K9-532AXSP04	309.1	490.4	372	419.8	-	310.9	489.1	371.8	418.5	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550K9-625AXSP04	353.8	549.4	420.6	472.8	-	355.2	547.9	420.7	471.3	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550K9-632AXSP04	336.4	528.2	402.6	452.8	-	338.2	526.2	402.4	451.5	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550R3-425AXSP02	245.9	439	318	369.4	775.8	257.3	443.6	324.8	374.2	773.9	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550R3-432AXSP02	224.9	408.3	293	341.7	725.6	236.2	412	299.5	346.2	722.7	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550R3-525AXSP04	335.7	529	402.3	453.1	-	337.3	527.5	402	452.4	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550R3-532AXSP04	315.1	500.6	379.3	428.3	-	317.1	498.7	379.4	427.2	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK550R3-625AXSP04	360.7	560.7	429.5	482.2	-	362.3	559.3	429.2	480.9	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK550R3-632AXSP04	342.9	539	410.5	461.8	-	344.9	537.2	410.5	460.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK750C4-425AXSP04	325.3	-	392.6	444.3	-	327.7	-	393	443.6	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK750C4-432AXSP04	301.1	483.6	364.2	412.9	-	303.2	483.1	364.7	412.5	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK750C4-525AXSP04	357.7	564	428.4	483.1	-	360	564.2	429.4	483	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK750C4-532AXSP04	336.3	535.2	404.9	456.9	-	338.2	534.4	405.2	456.8	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK750C4-632AXSP04	364.9	573.8	436.5	491.6	-	366.9	573.6	437.2	492	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK750C5-425AXSP04	325.3	-	392.6	444.3	-	327.7	-	393	443.6	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK750C5-432AXSP04	301.1	483.6	364.2	412.9	-	303.2	483.1	364.7	412.5	-	304	23.1	4"	244	18.4	3"	365	32.4	4"
EAW-FD1556ZK750C5-525AXSP04	357.7	564	428.4	483.1	-	360	564.2	429.4	483	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK750C5-532AXSP04	336.3	535.2	404.9	456.9	-	338.2	534.4	405.2	456.8	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK750C5-632AXSP04	364.9	573.8	436.5	491.6	-	366.9	573.6	437.2	492	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK750K2-425AXSP02	256.4	456.6	331.1	384.7	806.5	267.9	461.4	338.3	389.9	805.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK750K2-432AXSP02	234.8	424.4	305.3	355.7	755.1	245.8	428.8	312.2	360.4	752.9	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK750K2-525AXSP02	280.9	501.4	363	420.2	875.6	294.7	506.4	371.2	426.2	873.3	761	14	(2) 4"	609	9.2	(2) 4"	913	16.8	(3) 4"
EAW-FD1556ZK750K2-532AXSP04	326.8	520	393.3	444.4	-	329	518.7	393.8	443.8	-	378	24.4	4"	302	16.1	4"	453	30.4	(2) 4"
EAW-FD1556ZK750K2-625AXSP04	373.1	581.7	444.5	499.3	-	375.6	580.1	445.2	499	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK750K2-632AXSP04	355.5	559	425.8	479.3	-	357.9	557.8	425.6	478.7	-	456	22.1	(2) 4"	365	17.1	4"	548	31	(2) 4"
EAW-FD1556ZK750K3-425AXSP02	256.4	456.6	331.1	384.7	806.5	267.9	461.4	338.3	389.9	805.6	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK750K3-432AXSP02	234.8	424.4	305.3	355.7	755.1	245.8	428.8	312.2	360.4	752.9	609	12.7	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK750K3-525AXSP02	280.9	501.4	363	420.2	875.6	294.7	506.4	371.2	426.2	873.3	761	14	(2) 4"	609	9.2	(2) 4"	913	16.8	(3) 4"
EAW-FD1556ZK750K3-532AXSP04	326.8	520	393.3	444.4	-	329	518.7	393.8	443.8	-	378	24.4	4"	302	16.1	4"	453	30.4	

EAW-FD91S1WK177F7-425AXSP16	23.4	38.9	29	33.1	66.1	23.8	38.7	29	33	65.2	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK177F7-432AXSP16	21.6	36.2	26.8	30.7	62.1	21.9	36	26.9	30.6	61.3	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK177F7-525AXSP16	25.4	41.9	31.4	35.6	70.6	25.9	41.7	31.4	35.5	69.6	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK177F7-532AXSP16	23.7	39.5	29.4	33.5	67.3	24.1	39.3	29.5	33.4	66.2	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK177F7-625AXSP16	-	45.3	34.1	38.6	75.6	28.3	45	34.2	38.5	74.4	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK177F7-632AXSP16	-	43.3	32.4	36.8	73.1	-	43.1	32.5	36.8	71.9	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK24716-425AXSP16	25.8	42.6	31.9	36.3	72.7	26.1	42.4	31.9	36.2	71.7	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK24716-432AXSP16	23.6	39.6	29.4	33.6	68	24	39.5	29.5	33.5	67.2	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK24716-525AXSP16	28	46.1	34.5	39.2	77.8	28.4	45.9	34.5	39.1	76.8	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK24716-532AXSP16	26	43.3	32.2	36.8	73.9	26.5	43.2	32.3	36.7	72.8	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK24716-625AXSP16	30.7	50	37.6	42.7	83.5	31.2	49.7	37.7	42.5	82.3	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK24716-632AXSP16	28.9	47.7	35.6	40.6	80.6	29.4	47.5	35.8	40.5	79.4	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK320P5-425AXSP16	28.1	46.4	34.7	39.5	79.2	28.4	46.2	34.8	39.4	78.2	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK320P5-432AXSP16	25.6	42.8	31.8	36.4	73.7	26	42.7	31.9	36.3	72.8	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK320P5-525AXSP16	30.7	50.5	37.8	43.1	85.6	31.2	50.2	37.9	42.9	84.4	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK320P5-532AXSP16	28.4	47.2	35.1	40.1	80.6	28.8	47	35.2	40	79.5	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK320P5-625AXSP16	34	55.4	41.7	47.2	92.6	34.5	55	41.7	47	91.3	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK320P5-632AXSP16	31.7	52.5	39.2	44.6	88.6	32.3	52.2	39.3	44.5	87.4	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK320P7-425AXSP16	28.7	47.3	35.4	40.3	81	29.1	47.1	35.5	40.2	79.9	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK320P7-432AXSP16	26.2	43.7	32.5	37.2	75.3	26.6	43.5	32.6	37.1	74.4	56	21	1-1/2"	45	13.8	1-1/2"	68	29.5	1-1/2"
EAW-FD91S1WK320P7-525AXSP16	31.4	51.6	38.7	44	87.4	31.8	51.3	38.7	43.9	86.2	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK320P7-532AXSP16	29	48.2	35.9	41	82.3	29.4	48	36	40.9	81.2	68	22.5	1-1/2"	54	14.8	1-1/2"	81	27	2"
EAW-FD91S1WK320P7-625AXSP16	34.7	56.6	42.5	48.3	94.6	35.2	56.2	42.6	48	93.3	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S1WK320P7-632AXSP16	32.5	53.6	40	45.5	90.5	33	53.3	40.1	45.5	89.3	84	20.2	2"	68	16.6	1-1/2"	101	28.4	2"
EAW-FD91S2WK177F7-425AXSP12	50.6	79.5	60.5	68.2	-	50.5	78.6	60	67.5	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK177F7-432AXSP12	46.7	74	56.1	63.3	-	46.6	73.2	55.7	62.8	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK177F7-525AXSP12	55.8	86.6	66.5	74.7	143.7	55.7	85.8	66.1	73.9	141.3	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK177F7-532AXSP12	52.1	82	62.5	70.4	136.7	52.1	81.1	62.2	69.7	134.6	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK177F7-625AXSP16	63.4	95.7	74.3	82.8	-	63	94.3	73.4	81.6	-	84	33.4	2"	68	25.3	1-1/2"	101	46.8	2"
EAW-FD91S2WK177F7-632AXSP16	60.2	91.8	70.9	79.2	-	59.8	90.5	70.1	78.2	-	84	33.4	2"	68	25.3	1-1/2"	101	46.8	2"
EAW-FD91S2WK24716-425AXSP12	55.2	86.9	66.1	74.5	-	55.1	86.1	65.7	73.9	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK24716-432AXSP12	50.9	80.7	61.2	69.1	-	50.9	80	60.8	68.5	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK24716-525AXSP12	61.2	95.4	73	82	-	61.2	94.5	72.4	81.2	-	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK24716-532AXSP12	57.1	89.7	68.4	77	150.2	57.1	89	67.9	76.4	148	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK24716-625AXSP12	67.3	103.6	79.8	89.3	169.6	67.2	102.5	79.2	88.4	166.9	113	27.9	2"	90	18.4	2"	135	33.5	3"
EAW-FD91S2WK24716-632AXSP16	66.1	100.9	77.8	87	-	65.6	99.6	77.1	86	-	84	33.4	2"	68	25.3	1-1/2"	101	46.8	2"
EAW-FD91S2WK320P5-425AXSP12	59.9	94.6	71.8	81	-	59.8	93.7	71.4	80.3	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK320P5-432AXSP12	54.9	87.3	66.1	74.8	-	54.9	86.5	65.7	74.1	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK320P5-525AXSP12	66.9	104.5	79.8	89.8	-	66.9	103.5	79.2	88.9	-	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK320P5-532AXSP12	62.2	97.8	74.4	83.8	-	62	96.8	73.9	83.1	-	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK320P5-625AXSP12	74.4	114.6	88.1	98.7	-	74.2	113.3	87.4	97.6	185.2	113	27.9	2"	90	18.4	2"	135	33.5	3"
EAW-FD91S2WK320P5-632AXSP12	69.8	108.7	83.3	93.5	180.2	69.7	107.6	82.5	92.5	177.4	113	27.9	2"	90	18.4	2"	135	33.5	3"
EAW-FD91S2WK320P7-425AXSP12	61.1	96.6	73.3	82.7	-	61	95.7	72.9	81.9	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK320P7-432AXSP12	56	89.2	67.4	76.2	-	56	88.3	67	75.7	-	73	25	2"	59	19	1-1/2"	88	35.1	2"
EAW-FD91S2WK320P7-525AXSP12	68.3	106.7	81.4	91.6	-	68.1	105.7	81	90.7	-	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK320P7-532AXSP12	63.4	99.9	75.9	85.6	-	63.3	98.8	75.4	84.8	-	90	26.1	2"	72	17.2	2"	108	36.7	2"
EAW-FD91S2WK320P7-625AXSP12	75.8	116.9	89.8	100.6	-	75.6	115.7	89.2	99.7	-	113	27.9	2"	90	18.4	2"	135	33.5	3"
EAW-FD91S2WK320P7-632AXSP12	71.2	111	85	95.4	184.3	71.1	109.9	84.4	94.4	181.3	113	27.9	2"	90	18.4	2"	135	33.5	3"
EAW-FD91S3WK177F7-425AXSP08	76.8	120.5	91.7	103.4	-	76.7	119.2	91.1	102.4	-	113	26.8	2"	90	17.6	2"	135	32	3"
EAW-FD91S3WK177F7-432AXSP08	71	112.2	85.3	96.1	-	70.8	111.1	84.6	95.3	186.2	113	26.8	2"	90	17.6	2"	135	32	3"
EAW-FD91S3WK177F7-525AXSP08	85.3	132.5	101.6	113.9	218.7	85.2	131	100.8	112.8	215.1	141	23.3	3"	113	19.4	2"	169	32.7	3"
EAW-FD91S3WK177F7-532AXSP08	79.8	125.4	95.8	107.6	208.8	79.7	124	95	106.6	205.3	141	23.3	3"	113	19.4	2"	169	32.7	3"
EAW-FD91S3WK177F7-625AXSP08	91.4	140.8	108.5	121.5	229.9	91.3	139.1	107.6	120.1	225.8	169	24	3"	135	15.8	3"	203	33.7	3"
EAW-FD91S3WK177F7-632AXSP08	86.7	134.9	103.4	116.1	222.4	86.5	133.5	102.6	114.9	218.6	169	24	3"	135	15.8	3"	203	33.7	3"
EAW-FD91S3WK24716-425AXSP08	83.9	132	100.4	113	-	83.7	130.7	99.7	112.1	-	113	26.8	2"	90	17.6	2"	135	32	3"
EAW-FD91S3WK24716-432AXSP08	77.4	122.7	93	105	-	77.3	121.7	92.4	104.1	-	113	26.8	2"	90	17.6	2"	135	32	3"
EAW-FD91S3WK24716-525AXSP08	93.7	145.6	111.6	125.1	-	93.6	144.2	110.7	124	-	141	23.3	3"	113	19.4	2"	169	32.7	3"
EAW-FD91S3WK24716-532AXSP08	87.5	137.4	104.8	117.8	229.6	87.3	136	104.1	116.7	225.9	141	23.3	3"	113	19.4	2"	169	32.7	3"
EAW-FD91S3WK24716-625AXSP08	100.6	155.1	119.4	133.6	254.1	100.5	153.3	118.5	132.4	249.8	169	24	3"	135	15.8	3"	203	33.7	3"
EAW-FD91S3WK24716-632AXSP08	95.2	148.4	113.8	127.6	245.1	95.2	146.7	113	126.3	241.1	169	24	3"	135	15.8	3"	203	33.7	3"
EAW-FD91S3WK320P5-425AXSP08	91	143.5	109.1	123	-	90.8	142.3	108.4	121.9	-	113	26.8	2"	90	17.6	2"	135	32	3"
EAW-FD91S3WK320P5-432AXSP08	83.5	132.8	100.5	113.4	-	83.5	131.4	99.8	112.5	-	113	26.8	2"	90	17.6	2"	135	32	3"
EAW-FD91S3WK320P5-525AXSP08	102.5	159.6	122.2	137.1	-	102.2	158	121.2	135.9	-	141	23.3	3"	113	19.4	2"	169	32.7	3"
EAW-FD91S3WK320P5-532AXSP08	95.2	149.6	113.9	128.4	-	95.1	148.2	113.3	127.2	-	141	23.3	3"	113	19.4	2"	169	32.7	3"
EAW-FD91S3WK320P5-625AXSP08	111.3	171.5	131.8	147.7	281.9	111	169.6	130.8	146.2	277.1	169	24	3"	135	15.8	3"	203	33.7	3"
EAW-FD91S3WK320P5-632AXSP08	104.4	162.6	124.5	139.8	270	104.2	160.9	123.6	138.3	2									

EAW-FD915SWK177F7-632AXSP06	148.7	227.5	175.4	196.1	372.5	147.7	224.4	173.5	193.6	365.7	225	30	3"	180	19.8	3"	270	38.5	4"
EAW-FD915SWK24716-425AXSP04	134.1	214.9	162.7	183.8	363.4	134.7	213.2	162.1	182.6	358.2	225	21.3	3"	180	14	3"	270	26.3	4"
EAW-FD915SWK24716-432AXSP04	123.3	199.7	150.4	170.3	340	123.9	198.4	150.1	169.5	335.3	225	21.3	3"	180	14	3"	270	26.3	4"
EAW-FD915SWK24716-525AXSP06	158.9	244.3	187.9	210.3	-	157.9	241.3	186.2	207.9	-	186	28.8	3"	149	19	3"	223	40.5	3"
EAW-FD915SWK24716-532AXSP06	148.5	230.4	176.4	198	-	147.7	227.6	174.8	195.8	-	186	28.8	3"	149	19	3"	223	40.5	3"
EAW-FD915SWK24716-625AXSP06	171.9	261.3	202.2	225.5	-	170.9	258	200.2	222.9	-	225	30	3"	180	19.8	3"	270	38.5	4"
EAW-FD915SWK24716-632AXSP06	163	249.9	192.7	215.4	-	162.1	246.8	190.8	212.9	-	225	30	3"	180	19.8	3"	270	38.5	4"
EAW-FD915SWK320P5-425AXSP04	146.1	233.8	176.6	199.8	-	146.5	231.9	175.9	198.5	-	225	21.3	3"	180	14	3"	270	26.3	4"
EAW-FD915SWK320P5-432AXSP04	133.4	215.9	162.5	184.1	368.4	134.2	214.5	161.9	183.1	363.2	225	21.3	3"	180	14	3"	270	26.3	4"
EAW-FD915SWK320P5-523AXSP04	164	260.5	198	223.1	436.2	164.5	258.3	197.1	221.5	429.5	282	19.4	4"	225	15.4	3"	338	27.3	4"
EAW-FD915SWK320P5-532AXSP04	151.8	243.7	184.4	208.5	411.5	152.6	241.9	183.8	207.3	405.8	282	19.4	4"	225	15.4	3"	338	27.3	4"
EAW-FD915SWK320P5-625AXSP06	189.5	289	223.1	249.4	-	188.3	285.1	220.7	246.2	-	225	30	3"	180	19.8	3"	270	38.5	4"
EAW-FD915SWK320P5-632AXSP06	178.1	274.4	210.7	236.1	-	177.1	270.7	208.8	233.2	-	225	30	3"	180	19.8	3"	270	38.5	4"
EAW-FD915SWK320P7-425AXSP04	149	238.8	180.2	203.9	-	149.7	236.9	179.6	202.7	-	225	21.3	3"	180	14	3"	270	26.3	4"
EAW-FD915SWK320P7-432AXSP04	136.2	220.2	165.8	187.9	376.1	136.9	218.8	165.3	187	371	225	21.3	3"	180	14	3"	270	26.3	4"
EAW-FD915SWK320P7-525AXSP04	167.6	266	202	227.7	445.7	168.1	263.9	201.2	226.2	439.1	282	19.4	4"	225	15.4	3"	338	27.3	4"
EAW-FD915SWK320P7-532AXSP04	155.1	248.8	188.5	212.9	420.5	155.7	247.1	187.6	211.7	414.3	282	19.4	4"	225	15.4	3"	338	27.3	4"
EAW-FD915SWK320P7-625AXSP04	181.1	285.8	218.3	245.4	473.7	181.9	283.3	217.1	243.5	466.5	338	20.3	4"	270	13.4	4"	406	28.5	4"
EAW-FD915SWK320P7-632AXSP06	181.7	280.2	215.3	241	-	180.8	276.6	213.2	238.1	-	225	30	3"	180	19.8	3"	270	38.5	4"
EAW-FD915SWK177F7-432AXSP04	152	239.1	182	204.8	-	152.1	236.6	180.7	203.2	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK177F7-432AXSP04	140.3	222.7	169	190.6	375.3	140.1	220.5	167.7	188.9	369.2	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK177F7-525AXSP04	169	262.9	201.7	226.2	434.8	168.9	260.2	200.2	224.1	427.5	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK177F7-532AXSP04	158	248.6	189.7	213.5	414.4	158.2	246.2	188.5	211.3	408	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK177F7-625AXSP04	181.3	280	215.6	241.4	457.2	181.1	276.5	213.9	238.7	449.5	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK177F7-632AXSP04	171.8	268.1	205.1	230.6	442.2	171.6	264.9	203.6	228.3	434.7	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK24716-425AXSP04	166	261.6	199	224.2	-	166	259	197.8	222.3	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK24716-432AXSP04	153.1	243	184.3	208.2	-	153.1	240.9	183.2	206.3	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK24716-525AXSP04	185.8	289.2	221.2	248.4	-	185.6	286.1	219.8	246.3	-	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK24716-532AXSP04	173.2	272.4	207.6	233.9	455.5	173.2	270	206.5	231.7	448.7	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK24716-625AXSP04	199.5	308.2	237.1	265.4	505.3	199.3	304.8	235.5	263	496.8	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK24716-632AXSP04	188.7	294.4	225.5	253.1	487.2	188.6	291.5	224	250.9	479.3	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK320P5-425AXSP04	180	284.7	216.2	243.5	-	180	281.9	214.9	241.8	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK320P5-432AXSP04	165.2	262.8	199	224.7	-	165.1	260.5	197.7	223	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK320P5-525AXSP04	203.1	317.1	242.1	272.2	-	202.8	313.4	240.5	269.8	-	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK320P5-532AXSP04	188.5	297	225.9	254.4	-	188.3	293.8	224.3	252	-	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK320P5-625AXSP04	220.7	340.7	261.8	293.3	561.1	220	337.1	259.8	290.1	551.7	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK320P5-632AXSP04	206.8	323	247.2	277.2	536.6	206.4	319.7	245	274.7	527.5	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK320P7-425AXSP04	183.6	290.8	220.6	248.6	-	183.7	288	219.3	246.5	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK320P7-432AXSP04	168.5	268.5	203.1	229.4	-	168.5	266.3	201.9	227.8	-	225	24.6	3"	180	16.2	3"	270	30.9	4"
EAW-FD915SWK320P7-525AXSP04	207.1	323.8	247	277.8	-	207	320.3	245.6	275.5	-	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK320P7-532AXSP04	192.3	303.3	230.5	259.7	-	192.1	300.2	229	257.3	-	282	22.7	4"	225	17.6	3"	338	31.9	4"
EAW-FD915SWK320P7-625AXSP04	224.9	347.5	266.9	299	-	224.7	343.9	264.9	296.2	563.2	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-FD915SWK320P7-632AXSP04	210.9	329.8	252.1	283.3	548.1	210.7	326.1	250.2	280.5	539.1	338	23.6	4"	270	15.5	4"	406	33.1	4"
EAW-HD4053QY037M4-525AXSP02	-	1844.1	1343.1	1552.2	3204.5	1090.2	1851.1	1364.1	1561.9	3178.1	3156	14	6"	3030	10.1	6"	3787	19.7	6"
EAW-HD4053QY037M4-625AXSP02	-	1972.2	1441	1662.7	3407.6	-	1980.1	1464.7	1675.7	3375.4	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY037M4-632AXSP02	-	1865.8	1354.5	1567	3263.1	-	1874.9	1379.9	1581.3	3230.7	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY037K4-525AXSP02	-	1785	1297.6	1501.3	3101.8	-	1791.3	1319.7	1512.7	3071.6	3156	14	6"	3030	10.1	6"	3787	19.7	6"
EAW-HD4053QY037K4-625AXSP02	-	1903.5	1390.3	1605.9	3289.6	-	1913.4	1415	1618.1	3258.2	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY037K4-632AXSP02	-	1806.6	1309.1	1516.1	3155	-	1814.9	1335.4	1532	3123.3	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY045M4-525AXSP02	1098.4	1932.3	1406.5	1627.1	3359.9	1143.1	1940.6	1429.5	1638.2	3328.7	3156	14	6"	3030	10.1	6"	3787	19.7	6"
EAW-HD4053QY045M4-625AXSP02	-	2073	1514.2	1745.9	3578.3	-	2078.8	1539.6	1760	3544.5	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY045M4-632AXSP02	-	1957.2	1420.3	1644.6	3415.2	-	1964.7	1445.3	1657.8	3387	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY045K4-525AXSP02	1059.9	1868.1	1359.6	1571.8	3248.1	1103.4	1875.6	1381.2	1584.6	3217.5	3156	14	6"	3030	10.1	6"	3787	19.7	6"
EAW-HD4053QY045K4-625AXSP02	-	1998.2	1461.4	1684	3454.2	-	2006.5	1485.7	1700.1	3422	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY045K4-632AXSP02	-	1889.7	1373.4	1589.1	3302.5	-	1899.4	1397	1604.1	3274.7	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY055M4-525AXSP02	1177.3	2069.4	1506.5	1739.3	3593.3	1223.7	2077.2	1527.6	1753.1	3562.6	3156	14	6"	3030	10.1	6"	3787	19.7	6"
EAW-HD4053QY055M4-625AXSP02	1270.1	2218.9	1621.1	1868.6	3834.7	1322.5	2227.7	1648.1	1886.1	3797.2	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY055M4-632AXSP02	-	2094.3	1519.9	1759.5	3654.8	-	2101.2	1546	1775.6	3622.4	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY055K4-525AXSP02	1124.5	1976.6	1439.6	1663.3	3435.6	1170.1	1986.5	1461.6	1675.8	3410.4	3156	14	6"	3030	10.1	6"	3787	19.7	6"
EAW-HD4053QY055K4-625AXSP02	-	2115.1	1545.8	1783	3654.1	-	2125.9	1573.3	1799.1	3622.6	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-HD4053QY055K4-632AXSP02	-	2001.2	1453	1680.4	3495.6	-	2010.2	1479.7	1698	3464	3787	15.4	6"	3030	10.1	6"	4544	16.9	(2) 6"
EAW-VD1551PB370C2-425AXSP16	50.2	84.6	62.7	71.9	145.8	51.4	84.6	63.3	72	144.5	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB370C2-432AXSP16	46.1	78.9	58	66.7	136.7	47.3	78.8	58.5	66.9	135.5	113	19.6							



EAW-VD1551PB370K5-625AXSP16	56.5	94.2	70.2	80	159.1	58	94.2	70.8	80.3	157.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB370K5-632AXSP16	-	90.5	67	76.6	154.2	-	90.4	67.6	76.9	152.6	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB370K8-425AXSP16	48.2	81.5	60.3	69.1	140.2	49.4	81.5	60.8	69.3	138.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB370K8-432AXSP16	44.4	76	55.9	64.2	131.7	45.5	76.1	56.3	64.4	130.3	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB370K8-525AXSP16	52	87.5	64.8	74.1	148.9	53.3	87.4	65.4	74.3	147.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB370K8-532AXSP16	48.5	82.6	60.8	69.8	142	49.8	82.6	61.4	70	140.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB370K8-625AXSP16	56.5	94.2	70.2	80	159.1	58	94.2	70.8	80.3	157.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB370K8-632AXSP16	-	90.5	67	76.6	154.2	-	90.4	67.6	76.9	152.6	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400B3-425AXSP16	48.7	82.2	60.9	69.8	141.4	49.9	82.3	61.4	70	140.2	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400B3-432AXSP16	44.9	76.8	56.5	65	133.2	46.1	76.9	57	65.1	131.8	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400B3-525AXSP16	52.3	88.1	65.2	74.7	150	53.7	88.1	65.8	74.8	148.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400B3-532AXSP16	48.9	83.3	61.5	70.5	143.4	50.3	83.4	62	70.7	142.1	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400B3-625AXSP16	56.6	94.4	70.4	80.2	159.3	58.3	94.5	71.1	80.6	157.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400B3-632AXSP16	-	91.1	67.3	77.2	155.3	-	91.2	68.1	77.5	153.9	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400C3-425AXSP16	50.2	84.6	62.7	71.9	145.8	51.4	84.6	63.3	72	144.5	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400C3-432AXSP16	46.1	78.9	58	66.7	136.7	47.3	78.8	58.5	66.9	135.5	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400C3-525AXSP16	54.1	91	67.5	77.2	155.2	55.5	91	68.1	77.4	153.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400C3-532AXSP16	50.4	85.9	63.3	72.6	147.8	51.8	85.9	63.8	72.8	146.5	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400C3-625AXSP16	58.8	98.1	73.1	83.3	165.7	60.5	98.1	73.8	83.6	164	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400C3-632AXSP16	-	94.2	69.7	79.8	160.7	57.3	94.3	70.4	80.1	159.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400C9-425AXSP16	50.2	84.6	62.7	71.9	145.8	51.4	84.6	63.3	72	144.5	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400C9-432AXSP16	46.1	78.9	58	66.7	136.7	47.3	78.8	58.5	66.9	135.5	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400C9-525AXSP16	54.1	91	67.5	77.2	155.2	55.5	91	68.1	77.4	153.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400C9-532AXSP16	50.4	85.9	63.3	72.6	147.8	51.8	85.9	63.8	72.8	146.5	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400K3-425AXSP16	58.8	98.1	73.1	83.3	165.7	60.5	98.1	73.8	83.6	164	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400K3-432AXSP16	-	94.2	69.7	79.8	160.7	57.3	94.3	70.4	80.1	159.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400K3-525AXSP16	48.2	81.5	60.3	69.1	140.2	49.4	81.5	60.8	69.3	138.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400K3-532AXSP16	44.4	76	55.9	64.2	131.7	45.5	76.1	56.3	64.4	130.3	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400K3-525AXSP16	52	87.5	64.8	74.1	148.9	53.3	87.4	65.4	74.3	147.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400K3-532AXSP16	48.5	82.6	60.8	69.8	142	49.8	82.6	61.4	70	140.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400K3-625AXSP16	56.5	94.2	70.2	80	159.1	58	94.2	70.8	80.3	157.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400K3-632AXSP16	-	90.5	67	76.6	154.2	-	90.4	67.6	76.9	152.6	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400K9-425AXSP16	48.2	81.5	60.3	69.1	140.2	49.4	81.5	60.8	69.3	138.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400K9-432AXSP16	44.4	76	55.9	64.2	131.7	45.5	76.1	56.3	64.4	130.3	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400K9-525AXSP16	52	87.5	64.8	74.1	148.9	53.3	87.4	65.4	74.3	147.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400K9-532AXSP16	48.5	82.6	60.8	69.8	142	49.8	82.6	61.4	70	140.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400K9-625AXSP16	56.5	94.2	70.2	80	159.1	58	94.2	70.8	80.3	157.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400K9-632AXSP16	-	90.5	67	76.6	154.2	-	90.4	67.6	76.9	152.6	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400R3-425AXSP16	49.1	82.9	61.4	70.4	142.5	50.2	82.9	61.9	70.5	141.2	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400R3-432AXSP16	45.2	77.4	56.9	65.3	134	46.4	77.4	57.4	65.6	132.8	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB400R3-525AXSP16	52.9	89	65.9	75.4	151.6	54.2	89	66.4	75.5	150	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400R3-532AXSP16	49.3	84.1	61.9	71	144.5	50.6	84	62.5	71.3	143.2	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB400R3-625AXSP16	57.5	95.8	71.4	81.5	161.8	59.1	95.8	72	81.7	160	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB400R3-632AXSP16	-	92	68.1	78	157	-	92.1	68.8	78.2	155.2	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550B3-425AXSP16	53.4	89.8	66.7	76.4	155	54.6	90	67.3	76.6	153.8	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB550B3-432AXSP16	49.1	83.8	61.8	71	145.4	50.4	83.8	62.3	71.2	144.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB550B3-525AXSP16	57.4	96.4	71.6	81.8	164.5	58.9	96.4	72.2	82.1	163.3	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB550B3-532AXSP16	53.6	91.2	67.2	77.1	157.1	55	91.3	67.9	77.4	155.6	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB550B3-625AXSP16	62.3	103.8	77.2	88.1	175.1	64	104	78.1	88.6	173.7	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550B3-632AXSP16	59.1	99.9	73.9	84.6	170.4	60.9	100	74.7	84.9	169	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550C2-425AXSP16	56.3	94.6	70.4	80.4	163.5	57.6	94.8	70.8	80.7	162.2	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB550C2-432AXSP16	51.6	87.7	64.8	74.5	152.8	52.8	87.8	65.4	74.7	151.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB550C2-525AXSP16	61.1	102.2	76	87	174.8	62.4	102.3	76.7	87.2	173.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB550C2-532AXSP16	56.6	96.1	70.9	81.4	165.8	58	96.2	71.6	81.6	164.2	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB550C2-625AXSP16	66.7	111.2	82.8	94.5	187.9	68.4	111.2	83.5	94.7	186	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550C2-632AXSP16	62.9	106.2	78.5	89.9	181.3	64.6	106.2	79.4	90.3	179.5	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550C3-425AXSP16	56.3	94.6	70.4	80.4	163.5	57.6	94.8	70.8	80.7	162.2	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB550C3-432AXSP16	51.6	87.7	64.8	74.5	152.8	52.8	87.8	65.4	74.7	151.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD1551PB550C3-525AXSP16	61.1	102.2	76	87	174.8	62.4	102.3	76.7	87.2	173.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB550C3-532AXSP16	56.6	96.1	70.9	81.4	165.8	58	96.2	71.6	81.6	164.2	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB550C4-425AXSP16	66.7	111.2	82.8	94.5	187.9	68.4	111.2	83.5	94.7	186	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550C4-632AXSP16	62.9	106.2	78.5	89.9	181.3	64.6	106.2	79.4	90.3	179.5	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB550C5-425AXSP16	56.3	94.6	70.4	80.4	163.5	57.6	94.8	70.8	80.7	162.2	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.	

EAW-VD15S1PB550K4-532AXSP16	53.9	91.7	67.7	77.6	158	55.4	91.9	68.3	77.9	156.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K4-625AXSP16	63.3	105.4	78.5	89.5	177.9	64.8	105.3	79.1	89.7	176.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K4-632AXSP16	59.7	100.9	74.6	85.4	172.1	61.4	100.9	75.4	85.7	170.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K5-425AXSP16	53.7	90.4	67.1	76.8	156.1	54.9	90.5	67.6	77	154.6	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550K5-432AXSP16	49.4	84.1	62	71.3	146.1	50.5	84.1	62.5	71.5	144.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550K5-525AXSP16	58	97.2	72.2	82.5	166.1	59.4	97.3	72.8	82.9	164.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K5-532AXSP16	53.9	91.7	67.7	77.6	158	55.4	91.9	68.3	77.9	156.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K5-625AXSP16	63.3	105.4	78.5	89.5	177.9	64.8	105.3	79.1	89.7	176.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K5-632AXSP16	59.7	100.9	74.6	85.4	172.1	61.4	100.9	75.4	85.7	170.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K8-425AXSP16	53.7	90.4	67.1	76.8	156.1	54.9	90.5	67.6	77	154.6	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550K8-432AXSP16	49.4	84.1	62	71.3	146.1	50.5	84.1	62.5	71.5	144.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550K8-525AXSP16	58	97.2	72.2	82.5	166.1	59.4	97.3	72.8	82.9	164.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K8-532AXSP16	53.9	91.7	67.7	77.6	158	55.4	91.9	68.3	77.9	156.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K8-625AXSP16	63.3	105.4	78.5	89.5	177.9	64.8	105.3	79.1	89.7	176.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K8-632AXSP16	59.7	100.9	74.6	85.4	172.1	61.4	100.9	75.4	85.7	170.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K9-425AXSP16	53.7	90.4	67.1	76.8	156.1	54.9	90.5	67.6	77	154.6	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550K9-432AXSP16	49.4	84.1	62	71.3	146.1	50.5	84.1	62.5	71.5	144.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550K9-525AXSP16	58	97.2	72.2	82.5	166.1	59.4	97.3	72.8	82.9	164.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K9-532AXSP16	53.9	91.7	67.7	77.6	158	55.4	91.9	68.3	77.9	156.7	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550K9-625AXSP16	63.3	105.4	78.5	89.5	177.9	64.8	105.3	79.1	89.7	176.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550K9-632AXSP16	59.7	100.9	74.6	85.4	172.1	61.4	100.9	75.4	85.7	170.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550R3-425AXSP16	55.1	92.6	68.8	78.6	159.8	56.3	92.6	69.3	78.9	158.6	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550R3-432AXSP16	50.6	86.2	63.6	73	149.9	51.9	86.3	64.2	73.3	148.5	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB550R3-525AXSP16	59.4	99.6	74	84.6	170.3	60.8	99.6	74.6	84.9	168.9	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550R3-532AXSP16	55.3	93.8	69.3	79.5	161.9	56.7	94	69.9	79.8	160.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB550R3-625AXSP16	64.9	108.1	80.4	91.7	182.5	66.5	108	81.1	92	180.7	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB550R3-632AXSP16	61.2	103.4	76.4	87.5	176.4	62.9	103.5	77.2	87.8	174.9	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C2-425AXSP16	59.8	100.2	74.7	85.2	173.8	61.2	100.4	75.2	85.5	172.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C2-432AXSP16	54.8	93.1	68.8	78.9	162.1	56.1	93.3	69.4	79.2	160.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C2-525AXSP16	64.6	107.9	80.5	91.8	185	66.1	108.1	81.2	92.3	183.8	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C2-532AXSP16	60	101.6	75.1	86.2	175.5	61.5	101.9	75.9	86.6	174.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C2-632AXSP16	70.4	117.2	87.3	99.6	198.4	72.3	117.4	88.2	100.1	196.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C2-632AXSP16	66.5	112.3	83.1	95.1	191.7	68.3	112.4	83.9	95.5	190.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C3-425AXSP16	59.8	100.2	74.7	85.2	173.8	61.2	100.4	75.2	85.5	172.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C3-432AXSP16	54.8	93.1	68.8	78.9	162.1	56.1	93.3	69.4	79.2	160.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C3-525AXSP16	64.6	107.9	80.5	91.8	185	66.1	108.1	81.2	92.3	183.8	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C3-532AXSP16	60	101.6	75.1	86.2	175.5	61.5	101.9	75.9	86.6	174.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C3-625AXSP16	70.4	117.2	87.3	99.6	198.4	72.3	117.4	88.2	100.1	196.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C3-632AXSP16	66.5	112.3	83.1	95.1	191.7	68.3	112.4	83.9	95.5	190.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C4-425AXSP16	59.8	100.2	74.7	85.2	173.8	61.2	100.4	75.2	85.5	172.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C4-432AXSP16	54.8	93.1	68.8	78.9	162.1	56.1	93.3	69.4	79.2	160.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C4-525AXSP16	64.6	107.9	80.5	91.8	185	66.1	108.1	81.2	92.3	183.8	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C4-532AXSP16	60	101.6	75.1	86.2	175.5	61.5	101.9	75.9	86.6	174.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C4-625AXSP16	70.4	117.2	87.3	99.6	198.4	72.3	117.4	88.2	100.1	196.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C4-632AXSP16	66.5	112.3	83.1	95.1	191.7	68.3	112.4	83.9	95.5	190.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C5-425AXSP16	59.8	100.2	74.7	85.2	173.8	61.2	100.4	75.2	85.5	172.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C5-432AXSP16	54.8	93.1	68.8	78.9	162.1	56.1	93.3	69.4	79.2	160.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C5-525AXSP16	64.6	107.9	80.5	91.8	185	66.1	108.1	81.2	92.3	183.8	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C5-625AXSP16	70.4	117.2	87.3	99.6	198.4	72.3	117.4	88.2	100.1	196.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C5-632AXSP16	66.5	112.3	83.1	95.1	191.7	68.3	112.4	83.9	95.5	190.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C8-425AXSP16	59.8	100.2	74.7	85.2	173.8	61.2	100.4	75.2	85.5	172.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C8-432AXSP16	54.8	93.1	68.8	78.9	162.1	56.1	93.3	69.4	79.2	160.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C8-432AXSP16	64.6	107.9	80.5	91.8	185	66.1	108.1	81.2	92.3	183.8	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C8-532AXSP16	60	101.6	75.1	86.2	175.5	61.5	101.9	75.9	86.6	174.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C8-625AXSP16	70.4	117.2	87.3	99.6	198.4	72.3	117.4	88.2	100.1	196.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C8-632AXSP16	66.5	112.3	83.1	95.1	191.7	68.3	112.4	83.9	95.5	190.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C9-425AXSP16	59.8	100.2	74.7	85.2	173.8	61.2	100.4	75.2	85.5	172.4	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C9-432AXSP16	54.8	93.1	68.8	78.9	162.1	56.1	93.3	69.4	79.2	160.9	113	19.6	1-1/2"	90	12.9	1-1/2"	135	27.6	1-1/2"
EAW-VD15S1PB750C9-525AXSP16	64.6	107.9	80.5	91.8	185	66.1	108.1	81.2	92.3	183.8	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C9-532AXSP16	60	101.6	75.1	86.2	175.5	61.5	101.9	75.9	86.6	174.4	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD15S1PB750C9-625AXSP16	70.4	117.2	87.3	99.6	198.4	72.3	117.4	88.2	100.1	196.8	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750C9-632AXSP16	66.5	112.3	83.1	95.1	191.7	68.3	112.4	83.9	95.5	190.3	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD15S1PB750K2-425AXSP16	57.7	96.9																	

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1551PB750R3-525AXSP16	60.9	101.9	75.8	86.6	174.4	62.4	102	76.5	87	173.1	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB750R3-532AXSP16	56.7	96.1	71	81.5	165.8	58.2	96.3	71.7	81.9	164.6	135	21.2	1-1/2"	108	13.9	1-1/2"	162	25.1	2"
EAW-VD1551PB750R3-625AXSP16	66.3	110.4	82.2	93.8	186.5	68.1	110.5	83	94.2	185	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551PB750R3-632AXSP16	62.7	105.7	78.3	89.7	180.6	64.5	105.9	79.1	90	179.1	169	18.9	2"	135	15.8	1-1/2"	203	26.6	2"
EAW-VD1551P370C2-425AXSP16	62.1	99.7	75.5	85.3	168.2	62.4	98.9	75.2	84.7	165.7	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C2-432AXSP16	57.1	92.7	69.8	79.2	157.7	57.5	92.2	69.7	78.8	155.6	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C2-525AXSP16	67.4	107.5	81.6	92.3	179.7	67.8	106.7	81.4	91.6	177.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C2-532AXSP16	62.8	101.5	76.6	86.7	171	63.3	100.7	76.3	86.2	168.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C2-625AXSP16	73.8	116.6	88.8	100.1	192.3	74.2	115.6	88.5	99.3	189.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C2-632AXSP16	69.7	111.7	84.5	95.6	185.9	70.3	110.8	84.3	94.9	182.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C4-425AXSP16	62.1	99.7	75.5	85.3	168.2	62.4	98.9	75.2	84.7	165.7	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C4-432AXSP16	57.1	92.7	69.8	79.2	157.7	57.5	92.2	69.7	78.8	155.6	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C4-525AXSP16	67.4	107.5	81.6	92.3	179.7	67.8	106.7	81.4	91.6	177.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C4-532AXSP16	62.8	101.5	76.6	86.7	171	63.3	100.7	76.3	86.2	168.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C4-625AXSP16	73.8	116.6	88.8	100.1	192.3	74.2	115.6	88.5	99.3	189.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C4-632AXSP16	69.7	111.7	84.5	95.6	185.9	70.3	110.8	84.3	94.9	182.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C5-425AXSP16	62.1	99.7	75.5	85.3	168.2	62.4	98.9	75.2	84.7	165.7	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C5-432AXSP16	57.1	92.7	69.8	79.2	157.7	57.5	92.2	69.7	78.8	155.6	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C5-525AXSP16	67.4	107.5	81.6	92.3	179.7	67.8	106.7	81.4	91.6	177.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C5-532AXSP16	62.8	101.5	76.6	86.7	171	63.3	100.7	76.3	86.2	168.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C5-625AXSP16	73.8	116.6	88.8	100.1	192.3	74.2	115.6	88.5	99.3	189.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C5-632AXSP16	69.7	111.7	84.5	95.6	185.9	70.3	110.8	84.3	94.9	182.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C8-425AXSP16	62.1	99.7	75.5	85.3	168.2	62.4	98.9	75.2	84.7	165.7	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C8-432AXSP16	57.1	92.7	69.8	79.2	157.7	57.5	92.2	69.7	78.8	155.6	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370C8-525AXSP16	67.4	107.5	81.6	92.3	179.7	67.8	106.7	81.4	91.6	177.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C8-532AXSP16	62.8	101.5	76.6	86.7	171	63.3	100.7	76.3	86.2	168.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370C8-625AXSP16	73.8	116.6	88.8	100.1	192.3	74.2	115.6	88.5	99.3	189.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370C8-632AXSP16	69.7	111.7	84.5	95.6	185.9	70.3	110.8	84.3	94.9	182.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K2-425AXSP16	59.7	95.9	72.6	82.1	161.7	60	95.2	72.3	81.5	159.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K2-432AXSP16	55.1	89.5	67.4	76.5	152.1	55.5	88.9	67.2	76.1	150	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K2-525AXSP16	64.7	103.3	78.3	88.4	172.2	65.1	102.5	78.1	87.9	169.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K2-532AXSP16	60.4	97.7	73.6	83.5	164.1	60.9	96.8	73.4	83	161.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K2-625AXSP16	70.6	111.7	85.1	95.8	183.8	71.1	110.7	84.7	95	180.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K2-632AXSP16	66.9	107.2	81.1	91.6	178.2	67.5	106.3	80.8	91.1	175.3	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K4-425AXSP16	59.7	95.9	72.6	82.1	161.7	60	95.2	72.3	81.5	159.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K4-432AXSP16	55.1	89.5	67.4	76.5	152.1	55.5	88.9	67.2	76.1	150	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K4-525AXSP16	64.7	103.3	78.3	88.4	172.2	65.1	102.5	78.1	87.9	169.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K4-532AXSP16	60.4	97.7	73.6	83.5	164.1	60.9	96.8	73.4	83	161.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K4-625AXSP16	70.6	111.7	85.1	95.8	183.8	71.1	110.7	84.7	95	180.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K4-632AXSP16	66.9	107.2	81.1	91.6	178.2	67.5	106.3	80.8	91.1	175.3	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K5-425AXSP16	59.7	95.9	72.6	82.1	161.7	60	95.2	72.3	81.5	159.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K5-432AXSP16	55.1	89.5	67.4	76.5	152.1	55.5	88.9	67.2	76.1	150	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K5-525AXSP16	64.7	103.3	78.3	88.4	172.2	65.1	102.5	78.1	87.9	169.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K5-532AXSP16	60.4	97.7	73.6	83.5	164.1	60.9	96.8	73.4	83	161.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K5-625AXSP16	70.6	111.7	85.1	95.8	183.8	71.1	110.7	84.7	95	180.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K5-632AXSP16	66.9	107.2	81.1	91.6	178.2	67.5	106.3	80.8	91.1	175.3	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K8-425AXSP16	59.7	95.9	72.6	82.1	161.7	60	95.2	72.3	81.5	159.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K8-432AXSP16	55.1	89.5	67.4	76.5	152.1	55.5	88.9	67.2	76.1	150	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P370K8-525AXSP16	64.7	103.3	78.3	88.4	172.2	65.1	102.5	78.1	87.9	169.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K8-532AXSP16	60.4	97.7	73.6	83.5	164.1	60.9	96.8	73.4	83	161.7	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P370K8-625AXSP16	70.6	111.7	85.1	95.8	183.8	71.1	110.7	84.7	95	180.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P370K8-632AXSP16	66.9	107.2	81.1	91.6	178.2	67.5	106.3	80.8	91.1	175.3	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P400B3-425AXSP16	60.5	97.2	73.7	83.2	163.8	60.8	96.5	73.3	82.6	161.5	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P400B3-432AXSP16	55.8	90.8	68.3	77.5	154.1	56.3	90.1	68.1	77	152	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P400B3-525AXSP16	65.5	104.7	79.4	89.7	174.6	65.9	103.9	79.1	89.2	172.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P400B3-532AXSP16	61.2	98.9	74.6	84.6	166.4	61.7	98.2	74.5	84.1	164.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P400B3-625AXSP16	71.4	113.1	86	96.9	186	72	112.1	85.7	96.2	183.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P400B3-632AXSP16	67.8	108.7	82.2	92.8	180.7	68.4	107.8	82	92.3	177.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD1551P400C3-425AXSP16	62.1	99.7	75.5	85.3	168.2	62.4	98.9	75.2	84.7	165.7	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P400C3-432AXSP16	57.1	92.7	69.8	79.2	157.7	57.5	92.2	69.7	78.8	155.6	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD1551P400C3-525AXSP16	67.4	107.5	81.6	92.3	179.7	67.8	106.7	81.4	91.6	177.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD1551P400C3-532AXSP16	62.8	101.5	76.6	86.7	171	63.3	100.7	76.3	86.2</										

EAW-VD15S1PI550C3-432AXSP16	64.1	104	78.3	88.7	177.4	64.6	103.4	78.2	88.2	175.1	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C3-525AXSP16	76.2	121.5	92.3	104	203.9	76.6	120.7	92	103.4	201.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C3-532AXSP16	70.8	114	86.2	97.5	193	71.2	113.3	86	97	190.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C3-625AXSP16	83.9	132.6	101	113.8	219.4	84.3	131.5	100.7	113	216	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C3-632AXSP16	78.9	126.3	95.7	108.2	211.1	79.6	125.3	95.5	107.5	208.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C4-425AXSP16	69.9	112.1	84.7	95.8	-	70.2	111.3	84.4	95.2	187.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C4-432AXSP16	64.1	104	78.3	88.7	177.4	64.6	103.4	78.2	88.2	175.1	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C4-525AXSP16	76.2	121.5	92.3	104	203.9	76.6	120.7	92	103.4	201.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C4-532AXSP16	70.8	114	86.2	97.5	193	71.2	113.3	86	97	190.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C4-625AXSP16	83.9	132.6	101	113.8	219.4	84.3	131.5	100.7	113	216	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C4-632AXSP16	78.9	126.3	95.7	108.2	211.1	79.6	125.3	95.5	107.5	208.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C5-425AXSP16	69.9	112.1	84.7	95.8	-	70.2	111.3	84.4	95.2	187.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C5-432AXSP16	64.1	104	78.3	88.7	177.4	64.6	103.4	78.2	88.2	175.1	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C5-525AXSP16	76.2	121.5	92.3	104	203.9	76.6	120.7	92	103.4	201.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C5-532AXSP16	70.8	114	86.2	97.5	193	71.2	113.3	86	97	190.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C5-625AXSP16	83.9	132.6	101	113.8	219.4	84.3	131.5	100.7	113	216	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C5-632AXSP16	78.9	126.3	95.7	108.2	211.1	79.6	125.3	95.5	107.5	208.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C8-425AXSP16	69.9	112.1	84.7	95.8	-	70.2	111.3	84.4	95.2	187.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C8-432AXSP16	64.1	104	78.3	88.7	177.4	64.6	103.4	78.2	88.2	175.1	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C8-425AXSP16	76.2	121.5	92.3	104	203.9	76.6	120.7	92	103.4	201.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C8-532AXSP16	70.8	114	86.2	97.5	193	71.2	113.3	86	97	190.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C8-625AXSP16	83.9	132.6	101	113.8	219.4	84.3	131.5	100.7	113	216	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C8-632AXSP16	78.9	126.3	95.7	108.2	211.1	79.6	125.3	95.5	107.5	208.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C9-425AXSP16	69.9	112.1	84.7	95.8	-	70.2	111.3	84.4	95.2	187.4	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C9-432AXSP16	64.1	104	78.3	88.7	177.4	64.6	103.4	78.2	88.2	175.1	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550C9-525AXSP16	76.2	121.5	92.3	104	203.9	76.6	120.7	92	103.4	201.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C9-532AXSP16	70.8	114	86.2	97.5	193	71.2	113.3	86	97	190.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550C9-625AXSP16	83.9	132.6	101	113.8	219.4	84.3	131.5	100.7	113	216	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550C9-632AXSP16	78.9	126.3	95.7	108.2	211.1	79.6	125.3	95.5	107.5	208.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K2-425AXSP16	66.9	107.3	81.2	91.7	181.7	67.2	106.7	80.9	91.3	179.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K2-432AXSP16	61.6	100	75.2	85.2	170.2	62	99.4	75.2	84.9	168	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K2-432AXSP16	72.7	115.8	88	99.3	194.1	73.1	115.1	87.7	98.7	191.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K2-532AXSP16	67.7	109.1	82.5	93.4	184.4	68.2	108.5	82.2	92.9	181.9	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K2-625AXSP16	79.6	125.9	96	108	207.9	80.1	124.8	95.7	107.3	204.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K2-632AXSP16	75.2	120.4	91.1	103.1	201	75.8	119.5	90.9	102.5	197.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K3-425AXSP16	66.9	107.3	81.2	91.7	181.7	67.2	106.7	80.9	91.3	179.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K3-432AXSP16	61.6	100	75.2	85.2	170.2	62	99.4	75.2	84.9	168	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K3-532AXSP16	67.7	109.1	82.5	93.4	184.4	68.2	108.5	82.2	92.9	181.9	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K3-625AXSP16	79.6	125.9	96	108	207.9	80.1	124.8	95.7	107.3	204.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K3-632AXSP16	75.2	120.4	91.1	103.1	201	75.8	119.5	90.9	102.5	197.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K4-425AXSP16	66.9	107.3	81.2	91.7	181.7	67.2	106.7	80.9	91.3	179.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K4-432AXSP16	61.6	100	75.2	85.2	170.2	62	99.4	75.2	84.9	168	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K4-525AXSP16	72.7	115.8	88	99.3	194.1	73.1	115.1	87.7	98.7	191.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K4-532AXSP16	67.7	109.1	82.5	93.4	184.4	68.2	108.5	82.2	92.9	181.9	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K4-625AXSP16	79.6	125.9	96	108	207.9	80.1	124.8	95.7	107.3	204.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K4-632AXSP16	75.2	120.4	91.1	103.1	201	75.8	119.5	90.9	102.5	197.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K5-425AXSP16	66.9	107.3	81.2	91.7	181.7	67.2	106.7	80.9	91.3	179.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K5-432AXSP16	61.6	100	75.2	85.2	170.2	62	99.4	75.2	84.9	168	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K5-525AXSP16	72.7	115.8	88	99.3	194.1	73.1	115.1	87.7	98.7	191.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K5-532AXSP16	67.7	109.1	82.5	93.4	184.4	68.2	108.5	82.2	92.9	181.9	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K5-625AXSP16	79.6	125.9	96	108	207.9	80.1	124.8	95.7	107.3	204.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K5-632AXSP16	75.2	120.4	91.1	103.1	201	75.8	119.5	90.9	102.5	197.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K8-425AXSP16	66.9	107.3	81.2	91.7	181.7	67.2	106.7	80.9	91.3	179.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K8-432AXSP16	61.6	100	75.2	85.2	170.2	62	99.4	75.2	84.9	168	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K8-525AXSP16	72.7	115.8	88	99.3	194.1	73.1	115.1	87.7	98.7	191.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K8-532AXSP16	67.7	109.1	82.5	93.4	184.4	68.2	108.5	82.2	92.9	181.9	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K8-625AXSP16	79.6	125.9	96	108	207.9	80.1	124.8	95.7	107.3	204.8	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K8-632AXSP16	75.2	120.4	91.1	103.1	201	75.8	119.5	90.9	102.5	197.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PI550K9-425AXSP16	66.9	107.3	81.2	91.7	181.7	67.2	106.7	80.9	91.3	179.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K9-432AXSP16	61.6	100	75.2	85.2	170.2	62	99.4	75.2	84.9	168	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1PI550K9-532AXSP16	72.7	115.8	88	99.3	194.1	73.1	115.1	87.7	98.7	191.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K9-532AXSP16	67.7	109.1	82.5	93.4	184.4	68.2	108.5	82.2	92.9	181.9	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1PI550K9-625AXSP16	79.6	125.9	96	108	207.9	80.1</													

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1P1750C9-425AXSP16	74.9	120.2	90.7	102.7	-	75.4	119.6	90.6	102.2	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750C9-432AXSP16	68.8	111.6	83.9	95.2	-	69.3	110.9	83.7	94.7	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750C9-525AXSP16	81.6	130.1	98.7	111.4	218.8	82.2	129.3	98.6	111	216.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750C9-532AXSP16	75.9	122.2	92.4	104.5	207.2	76.5	121.5	92.3	104.1	204.6	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750C9-625AXSP16	89.8	141.7	108.2	121.8	235.5	90.4	140.8	107.9	121.1	232.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K3-632AXSP16	84.7	135.4	102.7	116	226.8	85.3	134.6	102.5	115.5	223.6	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K2-425AXSP16	72.5	116.1	87.7	99.2	-	72.9	115.5	87.6	98.8	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K2-432AXSP16	66.6	108	81.2	92	184.4	67.1	107.4	81.2	91.8	182.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K2-525AXSP16	78.8	125.6	95.3	107.4	211	79.3	124.7	95.1	107	208.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K2-532AXSP16	73.3	118.2	89.4	101	200.1	73.8	117.5	89.2	100.5	197.6	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K2-625AXSP16	86.3	136.4	104	117.2	226.2	86.9	135.6	103.9	116.7	223.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K2-632AXSP16	81.7	130.7	99	111.9	218.4	82.3	129.7	98.9	111.4	215.5	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K3-425AXSP16	72.5	116.1	87.7	99.2	-	72.9	115.5	87.6	98.8	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K3-432AXSP16	66.6	108	81.2	92	184.4	67.1	107.4	81.2	91.8	182.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K3-525AXSP16	78.8	125.6	95.3	107.4	211	79.3	124.7	95.1	107	208.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K3-532AXSP16	73.3	118.2	89.4	101	200.1	73.8	117.5	89.2	100.5	197.6	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K3-625AXSP16	86.3	136.4	104	117.2	226.2	86.9	135.6	103.9	116.7	223.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K3-632AXSP16	81.7	130.7	99	111.9	218.4	82.3	129.7	98.9	111.4	215.5	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K4-425AXSP16	72.5	116.1	87.7	99.2	-	72.9	115.5	87.6	98.8	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K4-432AXSP16	66.6	108	81.2	92	184.4	67.1	107.4	81.2	91.8	182.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K4-525AXSP16	78.8	125.6	95.3	107.4	211	79.3	124.7	95.1	107	208.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K4-532AXSP16	73.3	118.2	89.4	101	200.1	73.8	117.5	89.2	100.5	197.6	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K5-625AXSP16	86.3	136.4	104	117.2	226.2	86.9	135.6	103.9	116.7	223.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K5-632AXSP16	81.7	130.7	99	111.9	218.4	82.3	129.7	98.9	111.4	215.5	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K8-425AXSP16	72.5	116.1	87.7	99.2	-	72.9	115.5	87.6	98.8	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K8-432AXSP16	66.6	108	81.2	92	184.4	67.1	107.4	81.2	91.8	182.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K8-525AXSP16	78.8	125.6	95.3	107.4	211	79.3	124.7	95.1	107	208.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K8-532AXSP16	73.3	118.2	89.4	101	200.1	73.8	117.5	89.2	100.5	197.6	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K9-425AXSP16	81.7	130.7	99	111.9	218.4	82.3	129.7	98.9	111.4	215.5	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K9-432AXSP16	66.6	108	81.2	92	184.4	67.1	107.4	81.2	91.8	182.2	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750K9-525AXSP16	78.8	125.6	95.3	107.4	211	79.3	124.7	95.1	107	208.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K9-532AXSP16	73.3	118.2	89.4	101	200.1	73.8	117.5	89.2	100.5	197.6	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750K9-625AXSP16	86.3	136.4	104	117.2	226.2	86.9	135.6	103.9	116.7	223.2	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750K9-632AXSP16	81.7	130.7	99	111.9	218.4	82.3	129.7	98.9	111.4	215.5	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750R3-425AXSP16	70.9	113.7	85.8	97.1	-	71.4	113.1	85.7	96.7	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750R3-432AXSP16	65.3	105.8	79.7	90.2	180.7	65.7	105.3	79.6	89.9	178.5	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD15S1P1750R3-525AXSP16	77	122.7	93.1	105.1	205.9	77.6	122	93	104.5	203.3	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750R3-532AXSP16	71.7	115.6	87.3	98.8	195.8	72.3	114.9	87.3	98.4	193.1	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD15S1P1750R3-625AXSP16	84.3	133.1	101.5	114.4	220.5	84.9	132.3	101.4	113.8	217.5	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1P1750R3-632AXSP16	79.7	127.6	96.7	109.4	213.2	80.4	126.8	96.5	108.8	210.4	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD15S1PK370C2-425AXSP16	54.7	90.2	67.6	77	154.2	55.5	90	67.7	76.8	152.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C2-432AXSP16	50.3	84	62.5	71.5	144.5	51.1	83.8	62.7	71.4	143	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C2-525AXSP16	59.1	97.3	72.8	82.8	164.5	60.2	97	73	82.8	162.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C2-532AXSP16	55.1	91.8	68.3	77.9	156.6	56.1	91.5	68.6	77.8	154.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C2-625AXSP16	64.5	105.2	79.1	89.7	175.9	65.7	104.8	79.4	89.6	173.7	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD15S1PK370C2-632AXSP16	61	100.9	75.3	85.7	170.4	62.2	100.6	75.6	85.7	168.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD15S1PK370C4-425AXSP16	54.7	90.2	67.6	77	154.2	55.5	90	67.7	76.8	152.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C4-432AXSP16	50.3	84	62.5	71.5	144.5	51.1	83.8	62.7	71.4	143	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C4-525AXSP16	59.1	97.3	72.8	82.8	164.5	60.2	97	73	82.8	162.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C4-532AXSP16	55.1	91.8	68.3	77.9	156.6	56.1	91.5	68.6	77.8	154.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C4-625AXSP16	64.5	105.2	79.1	89.7	175.9	65.7	104.8	79.4	89.6	173.7	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD15S1PK370C4-632AXSP16	61	100.9	75.3	85.7	170.4	62.2	100.6	75.6	85.7	168.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD15S1PK370C5-425AXSP16	54.7	90.2	67.6	77	154.2	55.5	90	67.7	76.8	152.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C5-432AXSP16	50.3	84	62.5	71.5	144.5	51.1	83.8	62.7	71.4	143	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C5-525AXSP16	59.1	97.3	72.8	82.8	164.5	60.2	97	73	82.8	162.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C5-532AXSP16	55.1	91.8	68.3	77.9	156.6	56.1	91.5	68.6	77.8	154.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C5-625AXSP16	64.5	105.2	79.1	89.7	175.9	65.7	104.8	79.4	89.6	173.7	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD15S1PK370C5-632AXSP16	61	100.9	75.3	85.7	170.4	62.2	100.6	75.6	85.7	168.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD15S1PK370C8-425AXSP16	54.7	90.2	67.6	77	154.2	55.5	90	67.7	76.8	152.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C8-432AXSP16	50.3	84	62.5	71.5	144.5	51.1	83.8	62.7	71.4	143	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD15S1PK370C8-525AXSP16	59.1	97.3	72.8	82.8	164.5	60.2	97	73	82.8	162.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD15S1PK370C8-532AXSP16	55.1	91.8	68.3	77.9	156.6	56.1	91.5	68.6	77.8	154.7	135	22.5	1-1/						



EAW-VD1551PK400B3-632AXSP16	59.1	97.7	73	83.1	165	60.4	97.4	73.3	83.1	163	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400C3-425AXSP16	54.7	90.2	67.6	77	154.2	55.5	90	67.7	76.8	152.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400C3-432AXSP16	50.3	84	62.5	71.5	144.5	51.1	83.8	62.7	71.4	143	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400C3-525AXSP16	59.1	97.3	72.8	82.8	164.5	60.2	97	73	82.8	162.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400C3-532AXSP16	55.1	91.8	68.3	77.9	156.6	56.1	91.5	68.6	77.8	154.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400C3-625AXSP16	64.5	105.2	79.1	89.7	175.9	65.7	104.8	79.4	89.6	173.7	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400C3-632AXSP16	61	100.9	75.3	85.7	170.4	62.2	100.6	75.6	85.7	168.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400C9-425AXSP16	54.7	90.2	67.6	77	154.2	55.5	90	67.7	76.8	152.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400C9-432AXSP16	50.3	84	62.5	71.5	144.5	51.1	83.8	62.7	71.4	143	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400C9-525AXSP16	59.1	97.3	72.8	82.8	164.5	60.2	97	73	82.8	162.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400C9-532AXSP16	55.1	91.8	68.3	77.9	156.6	56.1	91.5	68.6	77.8	154.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400C9-625AXSP16	64.5	105.2	79.1	89.7	175.9	65.7	104.8	79.4	89.6	173.7	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400C9-632AXSP16	61	100.9	75.3	85.7	170.4	62.2	100.6	75.6	85.7	168.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400K3-425AXSP16	52.5	86.9	64.9	74.1	148.2	53.3	86.5	65.1	73.9	146.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400K3-432AXSP16	48.4	81	60.1	68.8	139.2	49.2	80.9	60.4	68.7	137.7	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400K3-525AXSP16	56.8	93.4	69.9	79.6	157.7	57.7	93	70.2	79.4	155.9	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400K3-532AXSP16	53	88.2	65.7	74.8	150.3	54	88	65.9	74.9	148.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400K9-632AXSP16	61.9	100.8	75.8	85.9	168.3	63	100.4	76	85.8	166.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400K3-632AXSP16	58.6	96.7	72.3	82.3	163.4	59.8	96.4	72.6	82.3	161.3	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400K9-425AXSP16	52.5	86.9	64.9	74.1	148.2	53.3	86.5	65.1	73.9	146.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400K9-432AXSP16	48.4	81	60.1	68.8	139.2	49.2	80.9	60.4	68.7	137.7	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400K9-525AXSP16	56.8	93.4	69.9	79.6	157.7	57.7	93	70.2	79.4	155.9	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400K9-532AXSP16	53	88.2	65.7	74.8	150.3	54	88	65.9	74.9	148.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400K9-625AXSP16	61.9	100.8	75.8	85.9	168.3	63	100.4	76	85.8	166.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400K9-632AXSP16	58.6	96.7	72.3	82.3	163.4	59.8	96.4	72.6	82.3	161.3	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400R3-425AXSP16	53.6	88.4	66.1	75.4	151	54.4	88.2	66.3	75.3	149.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400R3-432AXSP16	49.3	82.6	61.3	70.1	141.8	50.2	82.4	61.5	70.1	140.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK400R3-525AXSP16	57.7	95	71.1	81	160.6	58.8	94.7	71.4	81	158.9	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400R3-532AXSP16	53.9	89.9	66.9	76.4	153.3	54.9	89.7	67.1	76.3	151.4	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK400R3-625AXSP16	62.9	102.6	77.1	87.5	171.5	64.1	102.3	77.4	87.4	169.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK400R3-632AXSP16	59.6	98.6	73.6	83.8	166.3	60.8	98.2	74	83.7	164.3	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508B3-425AXSP16	58.4	96.3	72.1	82	165	59.3	96.1	72.4	81.9	163.2	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508B3-432AXSP16	53.7	89.7	66.7	76.3	154.6	54.6	89.5	67	76.2	153	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508B3-525AXSP16	63.1	103.5	77.7	88.4	175.4	64.1	103.3	77.9	88.2	173.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508B3-632AXSP16	58.8	97.7	72.9	83.2	167	59.9	97.7	73.2	83.2	165.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508B3-625AXSP16	68.6	112	84.1	95.4	187.1	69.9	111.7	84.5	95.5	185.1	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508B3-632AXSP16	65.1	107.6	80.4	91.4	181.8	66.4	107.3	80.7	91.5	179.7	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C2-425AXSP16	61.4	101.2	75.8	86.1	173.6	62.3	100.9	76.1	86	171.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C2-432AXSP16	56.3	93.8	69.9	79.7	162	57.2	93.7	70.1	79.7	160.2	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C2-525AXSP16	66.7	109.3	82.1	93.4	185.9	67.8	109.1	82.4	93.4	183.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C2-532AXSP16	61.9	102.8	76.6	87.6	175.9	63	102.5	76.9	87.5	174.1	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C2-625AXSP16	73.2	119.3	89.6	101.8	199.8	74.4	118.9	89.9	101.6	197.5	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C2-632AXSP16	68.9	113.8	85	96.8	192.4	70.2	113.5	85.3	96.8	190.4	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C3-425AXSP16	61.4	101.2	75.8	86.1	173.6	62.3	100.9	76.1	86	171.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C3-432AXSP16	56.3	93.8	69.9	79.7	162	57.2	93.7	70.1	79.7	160.2	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C3-525AXSP16	66.7	109.3	82.1	93.4	185.9	67.8	109.1	82.4	93.4	183.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C3-532AXSP16	61.9	102.8	76.6	87.6	175.9	63	102.5	76.9	87.5	174.1	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C3-625AXSP16	73.2	119.3	89.6	101.8	199.8	74.4	118.9	89.9	101.6	197.5	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C3-632AXSP16	68.9	113.8	85	96.8	192.4	70.2	113.5	85.3	96.8	190.4	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C4-425AXSP16	61.4	101.2	75.8	86.1	173.6	62.3	100.9	76.1	86	171.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C4-432AXSP16	56.3	93.8	69.9	79.7	162	57.2	93.7	70.1	79.7	160.2	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C4-525AXSP16	66.7	109.3	82.1	93.4	185.9	67.8	109.1	82.4	93.4	183.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C4-532AXSP16	61.9	102.8	76.6	87.6	175.9	63	102.5	76.9	87.5	174.1	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C4-625AXSP16	73.2	119.3	89.6	101.8	199.8	74.4	118.9	89.9	101.6	197.5	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C4-632AXSP16	68.9	113.8	85	96.8	192.4	70.2	113.5	85.3	96.8	190.4	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C5-425AXSP16	61.4	101.2	75.8	86.1	173.6	62.3	100.9	76.1	86	171.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C5-432AXSP16	56.3	93.8	69.9	79.7	162	57.2	93.7	70.1	79.7	160.2	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C5-525AXSP16	66.7	109.3	82.1	93.4	185.9	67.8	109.1	82.4	93.4	183.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C5-532AXSP16	61.9	102.8	76.6	87.6	175.9	63	102.5	76.9	87.5	174.1	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK508C5-625AXSP16	73.2	119.3	89.6	101.8	199.8	74.4	118.9	89.9	101.6	197.5	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C5-632AXSP16	68.9	113.8	85	96.8	192.4	70.2	113.5	85.3	96.8	190.4	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK508C8-425AXSP16	61.4	101.2	75.8	86.1	173.6	62.3	100.9	76.1	86	171.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK508C8-432AXSP16	56.3	93.8	69.9	79.7	162	57.2	93.7	70.1	79.7	160.2	113	21	1						

EAW-VD1551PK550K8-625AXSP16	69.3	113	84.9	96.4	189	70.6	112.7	85.3	96.3	186.8	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK550K8-632AXSP16	65.5	108.2	80.8	92.1	182.9	66.8	108	81.3	92	180.8	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK550K9-425AXSP16	58.7	96.7	72.4	82.3	165.5	59.5	96.4	72.7	82.4	163.9	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK550K9-432AXSP16	53.9	89.9	66.9	76.5	155	54.8	89.8	67.2	76.5	153.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK550K9-525AXSP16	63.5	104.1	78.1	88.9	176.7	64.5	103.9	78.4	88.8	174.7	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK550K9-532AXSP16	59.1	98.2	73.2	83.6	167.9	60.1	98.1	73.5	83.5	166.2	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK550K9-625AXSP16	69.3	113	84.9	96.4	189	70.6	112.7	85.3	96.3	186.8	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK550K9-632AXSP16	65.5	108.2	80.8	92.1	182.9	66.8	108	81.3	92	180.8	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK550R3-425AXSP16	60.2	99.2	74.4	84.5	170.1	61.1	99	74.6	84.4	168.2	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK550R3-432AXSP16	55.3	92.3	68.6	78.5	159.2	56.2	92	69	78.4	157.6	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK550R3-525AXSP16	65.1	106.7	80.1	91.1	181.1	66.2	106.6	80.5	91.1	179.4	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK550R3-532AXSP16	60.7	100.7	75.2	85.7	172.4	61.7	100.5	75.5	85.7	170.5	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK550R3-625AXSP16	71.1	116	87.1	98.9	194.2	72.4	115.6	87.6	98.9	192	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK550R3-632AXSP16	67.3	111.1	82.9	94.4	187.7	68.6	110.8	83.3	94.4	185.6	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C2-425AXSP16	65.5	107.6	80.5	91.6	185.2	66.5	107.5	80.9	91.7	183.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C2-432AXSP16	60	99.9	74.5	84.9	172.6	61	99.8	74.8	84.9	171	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C2-525AXSP16	71	116.1	87.3	99	197.7	72.1	116.1	87.6	99.2	195.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C2-532AXSP16	65.9	109.3	81.6	93.1	187.5	67.1	109.1	81.9	93.1	185.6	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C2-625AXSP16	77.7	126.3	95.1	108	212.2	79	126.1	95.7	108	210.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C2-632AXSP16	73.3	120.8	90.3	103	205	74.7	120.6	90.9	103	202.9	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C3-425AXSP16	65.5	107.6	80.5	91.6	185.2	66.5	107.5	80.9	91.7	183.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C3-432AXSP16	60	99.9	74.5	84.9	172.6	61	99.8	74.8	84.9	171	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C3-525AXSP16	71	116.1	87.3	99	197.7	72.1	116.1	87.6	99.2	195.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C3-532AXSP16	65.9	109.3	81.6	93.1	187.5	67.1	109.1	81.9	93.1	185.6	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C3-625AXSP16	77.7	126.3	95.1	108	212.2	79	126.1	95.7	108	210.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C3-632AXSP16	73.3	120.8	90.3	103	205	74.7	120.6	90.9	103	202.9	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C4-425AXSP16	65.5	107.6	80.5	91.6	185.2	66.5	107.5	80.9	91.7	183.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C4-432AXSP16	60	99.9	74.5	84.9	172.6	61	99.8	74.8	84.9	171	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C4-525AXSP16	71	116.1	87.3	99	197.7	72.1	116.1	87.6	99.2	195.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C4-532AXSP16	65.9	109.3	81.6	93.1	187.5	67.1	109.1	81.9	93.1	185.6	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C4-625AXSP16	77.7	126.3	95.1	108	212.2	79	126.1	95.7	108	210.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C4-632AXSP16	73.3	120.8	90.3	103	205	74.7	120.6	90.9	103	202.9	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C5-425AXSP16	65.5	107.6	80.5	91.6	185.2	66.5	107.5	80.9	91.7	183.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C5-432AXSP16	60	99.9	74.5	84.9	172.6	61	99.8	74.8	84.9	171	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C5-525AXSP16	71	116.1	87.3	99	197.7	72.1	116.1	87.6	99.2	195.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C5-532AXSP16	65.9	109.3	81.6	93.1	187.5	67.1	109.1	81.9	93.1	185.6	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C5-625AXSP16	77.7	126.3	95.1	108	212.2	79	126.1	95.7	108	210.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C5-632AXSP16	73.3	120.8	90.3	103	205	74.7	120.6	90.9	103	202.9	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C8-425AXSP16	65.5	107.6	80.5	91.6	185.2	66.5	107.5	80.9	91.7	183.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C8-432AXSP16	60	99.9	74.5	84.9	172.6	61	99.8	74.8	84.9	171	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C8-525AXSP16	71	116.1	87.3	99	197.7	72.1	116.1	87.6	99.2	195.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C8-532AXSP16	65.9	109.3	81.6	93.1	187.5	67.1	109.1	81.9	93.1	185.6	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C8-625AXSP16	77.7	126.3	95.1	108	212.2	79	126.1	95.7	108	210.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C8-632AXSP16	73.3	120.8	90.3	103	205	74.7	120.6	90.9	103	202.9	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C9-425AXSP16	65.5	107.6	80.5	91.6	185.2	66.5	107.5	80.9	91.7	183.4	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C9-432AXSP16	60	99.9	74.5	84.9	172.6	61	99.8	74.8	84.9	171	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750C9-525AXSP16	71	116.1	87.3	99	197.7	72.1	116.1	87.6	99.2	195.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C9-532AXSP16	65.9	109.3	81.6	93.1	187.5	67.1	109.1	81.9	93.1	185.6	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750C9-625AXSP16	77.7	126.3	95.1	108	212.2	79	126.1	95.7	108	210.2	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750C9-632AXSP16	73.3	120.8	90.3	103	205	74.7	120.6	90.9	103	202.9	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750K2-425AXSP16	63.3	104.1	77.9	88.6	178.8	64.2	104	78.3	88.7	177.1	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750K2-432AXSP16	58.1	96.7	72.2	82.2	167	59	96.5	72.4	82.3	165.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750K2-525AXSP16	68.4	112	84.2	95.6	190.4	69.6	112	84.5	95.7	188.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750K2-532AXSP16	63.7	105.7	78.8	90	181	64.8	105.6	79.2	90	179.2	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750K2-625AXSP16	74.7	121.8	91.6	104.1	204.2	76.1	121.5	92	104	202.1	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750K2-632AXSP16	70.7	116.5	87.2	99.2	197.5	72	116.4	87.6	99.3	195.4	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750K3-425AXSP16	63.3	104.1	77.9	88.6	178.8	64.2	104	78.3	88.7	177.1	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750K3-432AXSP16	58.1	96.7	72.2	82.2	167	59	96.5	72.4	82.3	165.5	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750K3-442AXSP16	68.4	112	84.2	95.6	190.4	69.6	112	84.5	95.7	188.8	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750K3-525AXSP16	63.7	105.7	78.8	90	181	64.8	105.6	79.2	90	179.2	135	22.5	1-1/2"	108	14.8	1-1/2"	162	27	2"
EAW-VD1551PK750K3-532AXSP16	74.7	121.8	91.6	104.1	204.2	76.1	121.5	92	104	202.1	169	20.2	2"	135	16.6	1-1/2"	203	28.4	2"
EAW-VD1551PK750K4-425AXSP16	63.3	104.1	77.9	88.6	178.8	64.2	104	78.3	88.7	177.1	113	21	1-1/2"	90	13.8	1-1/2"	135	29.5	1-1/2"
EAW-VD1551PK750K4-432AXSP16	58.1	96.7	72.2	82.2	167	59													

EAW-VD1551ZB370C4-532AXSP16	-	97.7	72	82.6	168.1	-	97.5	72.5	82.6	165.9	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370C4-625AXSP16	-	112.4	83.7	95.5	189.6	-	112.2	84.4	95.6	187	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370C4-632AXSP16	-	107.3	79.5	91	183.1	-	107.2	80.2	91	180.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370C5-425AXSP16	56	95.1	70.1	80.5	163.2	57.3	94.8	70.5	80.4	161.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370C5-432AXSP16	51.2	88.1	64.6	74.3	152.8	52.6	88	65.1	74.5	150.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370C5-525AXSP16	61.6	103.8	76.9	88	176.9	63.2	103.6	77.5	88.1	174.5	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370C5-532AXSP16	-	97.7	72	82.6	168.1	-	97.5	72.5	82.6	165.9	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370C5-625AXSP16	-	112.4	83.7	95.5	189.6	-	112.2	84.4	95.6	187	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370C5-632AXSP16	-	107.3	79.5	91	183.1	-	107.2	80.2	91	180.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370C8-425AXSP16	56	95.1	70.1	80.5	163.2	57.3	94.8	70.5	80.4	161.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370C8-432AXSP16	51.2	88.1	64.6	74.3	152.8	52.6	88	65.1	74.5	150.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370C8-525AXSP16	61.6	103.8	76.9	88	176.9	63.2	103.6	77.5	88.1	174.5	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370C8-532AXSP16	-	97.7	72	82.6	168.1	-	97.5	72.5	82.6	165.9	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370C8-625AXSP16	-	112.4	83.7	95.5	189.6	-	112.2	84.4	95.6	187	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370C8-632AXSP16	-	107.3	79.5	91	183.1	-	107.2	80.2	91	180.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K2-425AXSP16	53.8	91.3	67.5	77.3	156.8	55.1	91.2	67.9	77.3	155.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K2-432AXSP16	49.4	84.9	62.3	71.7	147.3	50.7	84.9	62.8	71.8	145.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K2-525AXSP16	-	99.6	73.8	84.5	169.5	60.6	99.3	74.3	84.5	167.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K2-532AXSP16	-	93.9	69.1	79.3	161.5	-	93.7	69.7	79.5	159.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K2-625AXSP16	-	107.6	80.1	91.3	181.5	-	107.2	80.8	91.4	178.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K2-632AXSP16	-	102.9	76.1	87.1	175.5	-	102.7	76.9	87.3	173.1	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K4-425AXSP16	53.8	91.3	67.5	77.3	156.8	55.1	91.2	67.9	77.3	155.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K4-432AXSP16	49.4	84.9	62.3	71.7	147.3	50.7	84.9	62.8	71.8	145.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K4-525AXSP16	-	99.6	73.8	84.5	169.5	60.6	99.3	74.3	84.5	167.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K4-532AXSP16	-	93.9	69.1	79.3	161.5	-	93.7	69.7	79.5	159.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K4-625AXSP16	-	107.6	80.1	91.3	181.5	-	107.2	80.8	91.4	178.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K4-632AXSP16	-	102.9	76.1	87.1	175.5	-	102.7	76.9	87.3	173.1	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K5-425AXSP16	53.8	91.3	67.5	77.3	156.8	55.1	91.2	67.9	77.3	155.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K5-432AXSP16	49.4	84.9	62.3	71.7	147.3	50.7	84.9	62.8	71.8	145.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K5-525AXSP16	-	99.6	73.8	84.5	169.5	60.6	99.3	74.3	84.5	167.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K5-532AXSP16	-	93.9	69.1	79.3	161.5	-	93.7	69.7	79.5	159.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K5-625AXSP16	-	107.6	80.1	91.3	181.5	-	107.2	80.8	91.4	178.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K5-632AXSP16	-	102.9	76.1	87.1	175.5	-	102.7	76.9	87.3	173.1	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K8-425AXSP16	53.8	91.3	67.5	77.3	156.8	55.1	91.2	67.9	77.3	155.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K8-432AXSP16	49.4	84.9	62.3	71.7	147.3	50.7	84.9	62.8	71.8	145.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB370K8-525AXSP16	-	99.6	73.8	84.5	169.5	60.6	99.3	74.3	84.5	167.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K8-532AXSP16	-	93.9	69.1	79.3	161.5	-	93.7	69.7	79.5	159.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB370K8-625AXSP16	-	107.6	80.1	91.3	181.5	-	107.2	80.8	91.4	178.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB370K8-632AXSP16	-	102.9	76.1	87.1	175.5	-	102.7	76.9	87.3	173.1	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400B3-425AXSP16	54.6	92.6	68.3	78.4	159.1	55.9	92.5	68.8	78.4	157.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400B3-432AXSP16	50.1	86.1	63.2	72.7	149.2	51.4	86.1	63.7	72.8	147.6	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400B3-525AXSP16	-	101	74.8	85.6	171.9	61.4	100.7	75.3	85.6	169.7	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400B3-532AXSP16	-	95.2	70	80.4	163.8	-	95	70.7	80.5	161.7	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400B3-625AXSP16	-	108.9	81.1	92.4	183.6	-	108.6	81.8	92.6	181.2	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400B3-632AXSP16	-	104.3	77.2	88.4	178	-	104.2	77.9	88.6	175.6	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400C3-425AXSP16	56	95.1	70.1	80.5	163.2	57.3	94.8	70.5	80.4	161.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400C3-432AXSP16	51.2	88.1	64.6	74.3	152.8	52.6	88	65.1	74.5	150.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400C3-525AXSP16	61.6	103.8	76.9	88	176.9	63.2	103.6	77.5	88.1	174.5	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400C3-532AXSP16	-	97.7	72	82.6	168.1	-	97.5	72.5	82.6	165.9	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400C3-625AXSP16	-	112.4	83.7	95.5	189.6	-	112.2	84.4	95.6	187	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400C3-632AXSP16	-	107.3	79.5	91	183.1	-	107.2	80.2	91	180.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400C9-425AXSP16	56	95.1	70.1	80.5	163.2	57.3	94.8	70.5	80.4	161.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400C9-432AXSP16	51.2	88.1	64.6	74.3	152.8	52.6	88	65.1	74.5	150.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400C9-525AXSP16	61.6	103.8	76.9	88	176.9	63.2	103.6	77.5	88.1	174.5	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400C9-532AXSP16	-	97.7	72	82.6	168.1	-	97.5	72.5	82.6	165.9	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400C9-625AXSP16	-	112.4	83.7	95.5	189.6	-	112.2	84.4	95.6	187	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400C9-632AXSP16	-	107.3	79.5	91	183.1	-	107.2	80.2	91	180.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400K3-425AXSP16	53.8	91.3	67.5	77.3	156.8	55.1	91.2	67.9	77.3	155.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400K3-432AXSP16	49.4	84.9	62.3	71.7	147.3	50.7	84.9	62.8	71.8	145.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400K3-525AXSP16	-	99.6	73.8	84.5	169.5	60.6	99.3	74.3	84.5	167.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400K3-532AXSP16	-	93.9	69.1	79.3	161.5	-	93.7	69.7	79.5	159.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB400K3-625AXSP16	-	107.6	80.1	91.3	181.5	-	107.2	80.8	91.4	178.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400K3-632AXSP16	-	102.9	76.1	87.1	175.5	-	102.7	76.9	87.3	173.1	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB400K9-425AXSP16	53.8	91.3	67.5	77.3	156.8	55.1	91.2	67.9	77.3	155.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400K9-432AXSP16	49.4	84.9	62.3	71.7	147.3	50.7	84.9	62.8	71.8	145.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB400K9-525AXSP16	-	99.6	73.8	84.5	169.5	60.6	99.3	74.3	84.5	167.3	180	19.5	2"	144	12.8	2"			

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1ZB550C5-525AXSP16	70	117.7	87.2	99.7	200.5	71.5	117.5	87.8	99.9	198.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550C5-532AXSP16	64.7	110.2	81.1	93.2	189.7	66.3	109.9	81.8	93.3	187.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550C5-625AXSP16	76.8	128.1	95.5	108.8	216.2	78.7	127.8	96	108.9	213.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550C5-632AXSP16	-	121.8	90.1	103.1	207.8	-	121.5	90.9	103.4	205.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550C8-425AXSP16	63.2	106.8	79.1	90.6	184.1	64.6	106.7	79.5	90.6	181.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550C8-432AXSP16	57.7	98.9	72.6	83.5	171.4	59.1	98.8	73.2	83.6	169.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550C8-525AXSP16	70	117.7	87.2	99.7	200.5	71.5	117.5	87.8	99.9	198.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550C8-532AXSP16	64.7	110.2	81.1	93.2	189.7	66.3	109.9	81.8	93.3	187.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550C8-625AXSP16	76.8	128.1	95.5	108.8	216.2	78.7	127.8	96	108.9	213.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550C8-632AXSP16	-	121.8	90.1	103.1	207.8	-	121.5	90.9	103.4	205.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550C9-425AXSP16	63.2	106.8	79.1	90.6	184.1	64.6	106.7	79.5	90.6	181.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550C9-432AXSP16	57.7	98.9	72.6	83.5	171.4	59.1	98.8	73.2	83.6	169.5	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550C9-525AXSP16	70	117.7	87.2	99.7	200.5	71.5	117.5	87.8	99.9	198.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550C9-532AXSP16	64.7	110.2	81.1	93.2	189.7	66.3	109.9	81.8	93.3	187.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550C9-625AXSP16	76.8	128.1	95.5	108.8	216.2	78.7	127.8	96	108.9	213.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550C9-632AXSP16	-	121.8	90.1	103.1	207.8	-	121.5	90.9	103.4	205.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K2-425AXSP16	60.4	102.5	75.7	86.7	176.2	61.8	102.2	76.1	86.8	174.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K2-432AXSP16	55.4	95	69.8	80.2	164.8	56.8	94.9	70.3	80.3	163.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K2-525AXSP16	66.5	112.1	83.1	95.1	191	68.2	111.9	83.7	95.1	188.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K2-532AXSP16	61.7	105.4	77.6	89.1	181.4	63.4	105.2	78.2	89.3	179.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K2-625AXSP16	-	121.6	90.5	103.2	205.3	-	121.2	91.1	103.3	202.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K2-632AXSP16	-	116	85.9	98.2	197.9	-	115.7	86.6	98.4	195.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K3-425AXSP16	60.4	102.5	75.7	86.7	176.2	61.8	102.2	76.1	86.8	174.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K3-432AXSP16	55.4	95	69.8	80.2	164.8	56.8	94.9	70.3	80.3	163.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K3-525AXSP16	66.5	112.1	83.1	95.1	191	68.2	111.9	83.7	95.1	188.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K3-532AXSP16	61.7	105.4	77.6	89.1	181.4	63.4	105.2	78.2	89.3	179.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K3-625AXSP16	-	121.6	90.5	103.2	205.3	-	121.2	91.1	103.3	202.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K3-632AXSP16	-	116	85.9	98.2	197.9	-	115.7	86.6	98.4	195.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K4-425AXSP16	60.4	102.5	75.7	86.7	176.2	61.8	102.2	76.1	86.8	174.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K4-432AXSP16	55.4	95	69.8	80.2	164.8	56.8	94.9	70.3	80.3	163.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K4-525AXSP16	66.5	112.1	83.1	95.1	191	68.2	111.9	83.7	95.1	188.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K4-532AXSP16	61.7	105.4	77.6	89.1	181.4	63.4	105.2	78.2	89.3	179.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K4-625AXSP16	-	121.6	90.5	103.2	205.3	-	121.2	91.1	103.3	202.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K4-632AXSP16	-	116	85.9	98.2	197.9	-	115.7	86.6	98.4	195.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K5-425AXSP16	60.4	102.5	75.7	86.7	176.2	61.8	102.2	76.1	86.8	174.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K5-432AXSP16	55.4	95	69.8	80.2	164.8	56.8	94.9	70.3	80.3	163.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K5-525AXSP16	66.5	112.1	83.1	95.1	191	68.2	111.9	83.7	95.1	188.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K5-532AXSP16	61.7	105.4	77.6	89.1	181.4	63.4	105.2	78.2	89.3	179.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K5-625AXSP16	-	121.6	90.5	103.2	205.3	-	121.2	91.1	103.3	202.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K5-632AXSP16	-	116	85.9	98.2	197.9	-	115.7	86.6	98.4	195.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K8-425AXSP16	60.4	102.5	75.7	86.7	176.2	61.8	102.2	76.1	86.8	174.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K8-432AXSP16	55.4	95	69.8	80.2	164.8	56.8	94.9	70.3	80.3	163.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K8-525AXSP16	66.5	112.1	83.1	95.1	191	68.2	111.9	83.7	95.1	188.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K8-532AXSP16	61.7	105.4	77.6	89.1	181.4	63.4	105.2	78.2	89.3	179.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K8-625AXSP16	-	121.6	90.5	103.2	205.3	-	121.2	91.1	103.3	202.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K8-632AXSP16	-	116	85.9	98.2	197.9	-	115.7	86.6	98.4	195.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K9-425AXSP16	60.4	102.5	75.7	86.7	176.2	61.8	102.2	76.1	86.8	174.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K9-432AXSP16	55.4	95	69.8	80.2	164.8	56.8	94.9	70.3	80.3	163.1	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550K9-525AXSP16	66.5	112.1	83.1	95.1	191	68.2	111.9	83.7	95.1	188.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K9-532AXSP16	61.7	105.4	77.6	89.1	181.4	63.4	105.2	78.2	89.3	179.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550K9-625AXSP16	-	121.6	90.5	103.2	205.3	-	121.2	91.1	103.3	202.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550K9-632AXSP16	-	116	85.9	98.2	197.9	-	115.7	86.6	98.4	195.4	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550R3-425AXSP16	62.2	105.2	77.9	89.3	181.2	63.6	105.1	78.4	89.4	179.2	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550R3-432AXSP16	56.9	97.7	71.7	82.4	169.4	58.4	97.6	72.3	82.7	167.4	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB550R3-525AXSP16	68.5	115.3	85.4	97.7	196.6	70.2	115.1	86	97.8	194.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550R3-532AXSP16	63.5	108.4	79.9	91.6	186.4	65.2	108.2	80.5	91.8	184.3	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB550R3-625AXSP16	-	125.2	93.2	106.3	211.2	77	124.8	93.8	106.4	208.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB550R3-632AXSP16	-	119.3	88.4	101.1	203.7	-	119.2	89	101.4	201.2	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB750C2-425AXSP16	68	114.6	84.9	97.3	197.7	69.4	114.5	85.4	97.6	195.6	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB750C2-432AXSP16	62.1	106.1	78.1	89.8	184.4	63.5	106	78.7	89.9	182.3	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD15S1ZB750C2-525AXSP16	75.2	126.1	93.5	107	215.5	76.8	126	94.2	107.2	213.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB750C2-532AXSP16	69.5	118.3	87.2	100	203.6	71.2	118.2	87.9	100.2	201.4	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD15S1ZB750C2-625AXSP16	82.4	137.5	102.4	116.8	232.2	84.5	137.2	103.1	116.9	229.6	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB750C2-632AXSP16	77.4	130.9	96.7	110.8	223.3	79.4	130.6	97.6	111	220.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD15S1ZB750C3-425AXSP16	68	114.6	84.9	97.3	197.7	69.4	114.5	85.4	97.6										

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1551ZB750K3-432AXSP16	60	102.7	75.6	86.8	178.4	61.5	102.7	76.2	87	176.7	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K3-525AXSP16	72.4	121.8	90.2	103.3	207.6	74.1	121.6	90.9	103.3	205.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K3-532AXSP16	67	114.3	84.3	96.5	196.7	68.8	114.2	84.9	96.9	194.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K3-625AXSP16	79.2	132.1	98.5	112.3	223.2	81.2	132.1	99.2	112.4	220.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K3-632AXSP16	-	126	93.3	106.8	215.3	76.6	125.9	94.1	107	212.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K4-425AXSP16	65.6	110.8	82	94.2	191	67.1	110.6	82.7	94.2	189	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K4-432AXSP16	60	102.7	75.6	86.8	178.4	61.5	102.7	76.2	87	176.7	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K4-525AXSP16	72.4	121.8	90.2	103.3	207.6	74.1	121.6	90.9	103.3	205.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K4-532AXSP16	67	114.3	84.3	96.5	196.7	68.8	114.2	84.9	96.9	194.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K4-625AXSP16	79.2	132.1	98.5	112.3	223.2	81.2	132.1	99.2	112.4	220.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K4-632AXSP16	-	126	93.3	106.8	215.3	76.6	125.9	94.1	107	212.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K5-425AXSP16	65.6	110.8	82	94.2	191	67.1	110.6	82.7	94.2	189	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K5-432AXSP16	60	102.7	75.6	86.8	178.4	61.5	102.7	76.2	87	176.7	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K5-525AXSP16	72.4	121.8	90.2	103.3	207.6	74.1	121.6	90.9	103.3	205.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K5-532AXSP16	67	114.3	84.3	96.5	196.7	68.8	114.2	84.9	96.9	194.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K5-625AXSP16	79.2	132.1	98.5	112.3	223.2	81.2	132.1	99.2	112.4	220.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K5-632AXSP16	-	126	93.3	106.8	215.3	76.6	125.9	94.1	107	212.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K8-425AXSP16	65.6	110.8	82	94.2	191	67.1	110.6	82.7	94.2	189	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K8-432AXSP16	60	102.7	75.6	86.8	178.4	61.5	102.7	76.2	87	176.7	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K8-432AXSP16	72.4	121.8	90.2	103.3	207.6	74.1	121.6	90.9	103.3	205.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K8-532AXSP16	67	114.3	84.3	96.5	196.7	68.8	114.2	84.9	96.9	194.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K8-625AXSP16	79.2	132.1	98.5	112.3	223.2	81.2	132.1	99.2	112.4	220.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K8-632AXSP16	-	126	93.3	106.8	215.3	76.6	125.9	94.1	107	212.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K9-425AXSP16	65.6	110.8	82	94.2	191	67.1	110.6	82.7	94.2	189	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K9-432AXSP16	60	102.7	75.6	86.8	178.4	61.5	102.7	76.2	87	176.7	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750K9-525AXSP16	72.4	121.8	90.2	103.3	207.6	74.1	121.6	90.9	103.3	205.2	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K9-532AXSP16	67	114.3	84.3	96.5	196.7	68.8	114.2	84.9	96.9	194.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750K9-625AXSP16	79.2	132.1	98.5	112.3	223.2	81.2	132.1	99.2	112.4	220.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750K9-632AXSP16	-	126	93.3	106.8	215.3	76.6	125.9	94.1	107	212.8	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750R3-425AXSP16	64.2	108.4	80.4	92	187	65.7	108.4	80.8	92.2	185	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750R3-432AXSP16	58.8	100.8	74	85.1	174.6	60.3	100.6	74.6	85.3	172.9	146	18.4	2"	117	14.8	1-1/2"	176	25.8	2"
EAW-VD1551ZB750R3-525AXSP16	70.7	119	88.2	100.8	202.9	72.4	118.8	88.8	100.9	200.6	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750R3-532AXSP16	65.6	111.8	82.4	94.5	192.5	67.3	111.7	83.1	94.6	190.4	180	19.5	2"	144	12.8	2"	216	27.4	2"
EAW-VD1551ZB750R3-625AXSP16	77.2	128.8	96	109.4	217.6	79.3	128.6	96.7	109.7	215.2	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZB750R3-632AXSP16	-	123.1	91.1	104.3	210.2	-	123	91.9	104.5	207.7	225	21.3	2"	180	14.1	2"	270	24	3"
EAW-VD1551ZK017G7-425AXSP16	87.9	144.7	108.3	123.2	-	89.1	144.1	108.5	123	-	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK017G7-432AXSP16	79.8	132.8	99	112.9	230.3	80.9	132.6	99.2	112.7	227.6	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK017G7-525AXSP16	98.5	161.1	121.2	137.5	275	99.7	160.5	121.3	137.2	271.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK017G7-532AXSP16	90.4	149.9	111.9	127.5	257.3	91.7	149.2	112.2	127.2	254.3	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK017G7-625AXSP16	109.8	178.3	134.4	152.5	300.3	111.2	177.5	134.6	152	296.4	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK017G7-632AXSP16	102	168	125.8	143.3	285.3	103.6	167.2	126	142.9	281.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C2-432AXSP16	60.5	100.4	74.8	85.4	171	61.4	100	75	85.1	168.6	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C2-432AXSP16	55.5	93.4	69.1	79	160.1	56.4	92.8	69.3	78.8	158	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C2-525AXSP16	66.7	109.9	82.2	93.6	185.4	67.8	109.2	82.3	93.2	182.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C2-532AXSP16	61.9	103.4	76.8	87.7	176.2	63.1	102.9	77	87.5	173.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C2-625AXSP16	-	119	89.5	101.5	198.6	-	118.3	89.7	101.2	195.5	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C2-632AXSP16	-	113.7	84.9	96.6	191.7	-	113.1	85.2	96.4	188.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C4-425AXSP16	60.5	100.4	74.8	85.4	171	61.4	100	75	85.1	168.6	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C4-432AXSP16	55.5	93.4	69.1	79	160.1	56.4	92.8	69.3	78.8	158	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C4-525AXSP16	66.7	109.9	82.2	93.6	185.4	67.8	109.2	82.3	93.2	182.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C4-532AXSP16	61.9	103.4	76.8	87.7	176.2	63.1	102.9	77	87.5	173.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C4-625AXSP16	-	119	89.5	101.5	198.6	-	118.3	89.7	101.2	195.5	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C4-632AXSP16	-	113.7	84.9	96.6	191.7	-	113.1	85.2	96.4	188.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C5-425AXSP16	60.5	100.4	74.8	85.4	171	61.4	100	75	85.1	168.6	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C5-432AXSP16	55.5	93.4	69.1	79	160.1	56.4	92.8	69.3	78.8	158	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C5-525AXSP16	66.7	109.9	82.2	93.6	185.4	67.8	109.2	82.3	93.2	182.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C5-532AXSP16	61.9	103.4	76.8	87.7	176.2	63.1	102.9	77	87.5	173.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C5-625AXSP16	-	119	89.5	101.5	198.6	-	118.3	89.7	101.2	195.5	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C5-632AXSP16	-	113.7	84.9	96.6	191.7	-	113.1	85.2	96.4	188.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK370C8-425AXSP16	60.5	100.4	74.8	85.4	171	61.4	100	75	85.1	168.6	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C8-432AXSP16	55.5	93.4	69.1	79	160.1	56.4	92.8	69.3	78.8	158	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK370C8-525AXSP16	66.7	109.9	82.2	93.6	185.4	67.8	109.2	82.3	93.2	182.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C8-532AXSP16	61.9	103.4	76.8	87.7	176.2	63.1	102.9	77	87.5	173.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK370C8-625AXSP16	-	119	89.5	101.5	198.6	-	118.3	89.7	101.2	195.5	225	22.7	2						

EAW-VD1551ZK400C9-425AXSP16	60.5	100.4	74.8	85.4	171	61.4	100	75	85.1	168.6	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400C9-432AXSP16	55.5	93.4	69.1	79	160.1	56.4	92.8	69.3	78.8	158	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400C9-525AXSP16	66.7	109.9	82.2	93.6	185.4	67.8	109.2	82.3	93.2	182.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400C9-532AXSP16	61.9	103.4	76.8	87.7	176.2	63.1	102.9	77	87.5	173.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400C9-625AXSP16	-	119	89.5	101.5	198.6	-	118.3	89.7	101.2	195.5	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400C9-632AXSP16	-	113.7	84.9	96.6	191.7	-	113.1	85.2	96.4	188.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400K3-425AXSP16	58.1	96.8	72	82.1	164.6	59.1	96.2	72.1	81.9	162.3	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400K3-432AXSP16	53.5	90	66.6	76.2	154.6	54.5	89.6	66.9	76.1	152.3	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400K3-525AXSP16	63.9	105.4	78.8	89.7	177.6	65	104.9	79.1	89.4	175	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400K3-532AXSP16	-	99.5	73.9	84.4	169.3	60.8	99	74.2	84.3	166.9	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400K3-625AXSP16	-	113.8	85.5	97.1	189.9	-	113.1	85.8	96.8	186.9	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400K3-632AXSP16	-	108.9	81.4	92.7	183.9	-	108.3	81.7	92.5	180.9	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400K9-425AXSP16	58.1	96.8	72	82.1	164.6	59.1	96.2	72.1	81.9	162.3	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400K9-432AXSP16	53.5	90	66.6	76.2	154.6	54.5	89.6	66.9	76.1	152.3	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400K9-525AXSP16	63.9	105.4	78.8	89.7	177.6	65	104.9	79.1	89.4	175	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400K9-532AXSP16	-	99.5	73.9	84.4	169.3	60.8	99	74.2	84.3	166.9	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400K9-625AXSP16	-	113.8	85.5	97.1	189.9	-	113.1	85.8	96.8	186.9	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400K9-632AXSP16	-	108.9	81.4	92.7	183.9	-	108.3	81.7	92.5	180.9	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400R3-425AXSP16	59.5	98.9	73.6	84	168.3	60.5	98.4	73.8	83.8	166	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400R3-432AXSP16	54.7	92	68.1	78	157.9	55.7	91.6	68.3	77.8	155.9	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK400R3-525AXSP16	65.4	107.7	80.5	91.6	181.7	66.5	107.1	80.8	91.4	179.1	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400R3-532AXSP16	60.9	101.6	75.5	86.3	173	62.1	101.1	75.8	86.1	170.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK400R3-625AXSP16	-	116.4	87.5	99.1	194.1	-	115.6	87.7	98.9	191.1	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK400R3-632AXSP16	-	111.3	83.2	94.8	187.9	-	110.8	83.5	94.6	185.1	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550B3-425AXSP16	65.3	108.2	80.8	92.1	184.9	66.3	107.7	80.9	91.9	182.2	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550B3-432AXSP16	59.9	100.6	74.6	85.2	172.9	60.9	100.2	74.8	85.2	170.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550B3-525AXSP16	72	118.7	88.8	101	200.3	73.2	118.2	88.9	100.7	197.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550B3-532AXSP16	66.9	111.7	83	94.7	190.3	68.1	111.1	83.3	94.5	187.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550B3-625AXSP16	78.8	128.6	96.5	109.5	214.7	80.2	127.8	96.9	109.4	211.5	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550B3-632AXSP16	-	122.9	91.8	104.4	207.3	75.8	122.2	92.1	104.3	204.5	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C2-425AXSP16	68.3	113.2	84.4	96.4	193.4	69.2	112.6	84.6	96.1	190.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C2-432AXSP16	62.4	104.7	77.7	88.9	180	63.5	104.4	77.9	88.6	177.7	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C2-525AXSP16	75.7	124.6	93.3	106.2	210.6	76.8	124	93.4	105.8	207.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C2-532AXSP16	70	116.9	86.8	99.1	199.2	71.3	116.3	87.1	98.9	196.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C2-625AXSP16	83.2	135.9	102	115.8	226.9	84.6	135.1	102.2	115.4	223.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C2-632AXSP16	78.1	129.1	96.5	109.8	218.2	79.5	128.4	96.7	109.5	215	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C3-425AXSP16	68.3	113.2	84.4	96.4	193.4	69.2	112.6	84.6	96.1	190.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C3-432AXSP16	62.4	104.7	77.7	88.9	180	63.5	104.4	77.9	88.6	177.7	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C3-525AXSP16	75.7	124.6	93.3	106.2	210.6	76.8	124	93.4	105.8	207.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C3-625AXSP16	83.2	135.9	102	115.8	226.9	84.6	135.1	102.2	115.4	223.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C3-632AXSP16	78.1	129.1	96.5	109.8	218.2	79.5	128.4	96.7	109.5	215	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C4-425AXSP16	68.3	113.2	84.4	96.4	193.4	69.2	112.6	84.6	96.1	190.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C4-432AXSP16	62.4	104.7	77.7	88.9	180	63.5	104.4	77.9	88.6	177.7	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C4-525AXSP16	75.7	124.6	93.3	106.2	210.6	76.8	124	93.4	105.8	207.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C4-532AXSP16	70	116.9	86.8	99.1	199.2	71.3	116.3	87.1	98.9	196.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C4-625AXSP16	83.2	135.9	102	115.8	226.9	84.6	135.1	102.2	115.4	223.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C4-632AXSP16	78.1	129.1	96.5	109.8	218.2	79.5	128.4	96.7	109.5	215	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C5-425AXSP16	68.3	113.2	84.4	96.4	193.4	69.2	112.6	84.6	96.1	190.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C5-432AXSP16	62.4	104.7	77.7	88.9	180	63.5	104.4	77.9	88.6	177.7	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C5-525AXSP16	75.7	124.6	93.3	106.2	210.6	76.8	124	93.4	105.8	207.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C5-625AXSP16	70	116.9	86.8	99.1	199.2	71.3	116.3	87.1	98.9	196.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C5-632AXSP16	83.2	135.9	102	115.8	226.9	84.6	135.1	102.2	115.4	223.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C5-632AXSP16	78.1	129.1	96.5	109.8	218.2	79.5	128.4	96.7	109.5	215	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C8-425AXSP16	68.3	113.2	84.4	96.4	193.4	69.2	112.6	84.6	96.1	190.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C8-432AXSP16	62.4	104.7	77.7	88.9	180	63.5	104.4	77.9	88.6	177.7	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C8-525AXSP16	75.7	124.6	93.3	106.2	210.6	76.8	124	93.4	105.8	207.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C8-532AXSP16	70	116.9	86.8	99.1	199.2	71.3	116.3	87.1	98.9	196.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C8-625AXSP16	83.2	135.9	102	115.8	226.9	84.6	135.1	102.2	115.4	223.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C8-632AXSP16	78.1	129.1	96.5	109.8	218.2	79.5	128.4	96.7	109.5	215	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550C9-425AXSP16	68.3	113.2	84.4	96.4	193.4	69.2	112.6	84.6	96.1	190.8	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C9-432AXSP16	62.4	104.7	77.7	88.9	180	63.5	104.4	77.9	88.6	177.7	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550C9-525AXSP16	75.7	124.6	93.3	106.2	210.6	76.8	124	93.4	105.8	207.6	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C9-532AXSP16	70	116.9	86.8	99.1	199.2	71.3	116.3	87.1	98.9	196.5	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550C9-625AXSP16	83.2	135.9	102	115.8	226.9														

EAW-VD1551ZK550K9-632AXSP16	-	123.1	72	104.8	208	75.9	122.6	92.3	104.5	204.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550R3-425AXSP16	67.5	111.7	83.4	95.2	190.7	68.5	111.3	83.6	95	188.4	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550R3-432AXSP16	61.8	103.6	76.9	88	178.4	62.9	103.4	77.1	87.9	176.3	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK550R3-525AXSP16	74.4	122.5	91.6	104.3	206.9	75.6	122	91.8	104	204.2	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550R3-532AXSP16	69.1	115.3	85.7	97.8	196.3	70.3	114.7	86	97.7	193.9	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK550R3-625AXSP16	81.5	132.9	99.9	113.4	222	82.8	132.3	100.2	113.1	219	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK550R3-632AXSP16	76.7	126.9	94.7	107.8	214.4	78.2	126.3	95.1	107.8	211.2	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C2-425AXSP16	73.7	121.7	91.1	103.8	208.6	74.7	121.3	91.2	103.4	206.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C2-432AXSP16	67.3	112.7	83.7	95.9	194.3	68.5	112.4	84	95.8	192.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C2-532AXSP16	81.5	134.2	100.4	114.5	227.2	82.8	133.5	100.7	114.1	224.4	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C2-625AXSP16	89.7	146.4	109.9	124.8	244.8	91.3	145.7	110.3	124.5	241.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C2-632AXSP16	84.2	139.4	104	118.5	235.4	85.8	138.6	104.4	118.2	232.4	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C3-425AXSP16	73.7	121.7	91.1	103.8	208.6	74.7	121.3	91.2	103.4	206.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C3-432AXSP16	67.3	112.7	83.7	95.9	194.3	68.5	112.4	84	95.8	192.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C3-525AXSP16	81.5	134.2	100.4	114.5	227.2	82.8	133.5	100.7	114.1	224.4	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C3-532AXSP16	75.6	125.8	93.6	106.9	214.8	76.9	125.3	93.9	106.8	212.2	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C3-625AXSP16	89.7	146.4	109.9	124.8	244.8	91.3	145.7	110.3	124.5	241.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C3-632AXSP16	84.2	139.4	104	118.5	235.4	85.8	138.6	104.4	118.2	232.4	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C4-425AXSP16	73.7	121.7	91.1	103.8	208.6	74.7	121.3	91.2	103.4	206.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C4-432AXSP16	67.3	112.7	83.7	95.9	194.3	68.5	112.4	84	95.8	192.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C4-532AXSP16	81.5	134.2	100.4	114.5	227.2	82.8	133.5	100.7	114.1	224.4	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C4-625AXSP16	89.7	146.4	109.9	124.8	244.8	91.3	145.7	110.3	124.5	241.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C5-425AXSP16	73.7	121.7	91.1	103.8	208.6	74.7	121.3	91.2	103.4	206.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C5-432AXSP16	67.3	112.7	83.7	95.9	194.3	68.5	112.4	84	95.8	192.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C5-525AXSP16	81.5	134.2	100.4	114.5	227.2	82.8	133.5	100.7	114.1	224.4	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C5-532AXSP16	75.6	125.8	93.6	106.9	214.8	76.9	125.3	93.9	106.8	212.2	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C5-625AXSP16	89.7	146.4	109.9	124.8	244.8	91.3	145.7	110.3	124.5	241.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C5-632AXSP16	84.2	139.4	104	118.5	235.4	85.8	138.6	104.4	118.2	232.4	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C8-425AXSP16	73.7	121.7	91.1	103.8	208.6	74.7	121.3	91.2	103.4	206.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C8-432AXSP16	67.3	112.7	83.7	95.9	194.3	68.5	112.4	84	95.8	192.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C8-525AXSP16	81.5	134.2	100.4	114.5	227.2	82.8	133.5	100.7	114.1	224.4	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C8-532AXSP16	75.6	125.8	93.6	106.9	214.8	76.9	125.3	93.9	106.8	212.2	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C8-625AXSP16	89.7	146.4	109.9	124.8	244.8	91.3	145.7	110.3	124.5	241.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C9-425AXSP16	73.7	121.7	91.1	103.8	208.6	74.7	121.3	91.2	103.4	206.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C9-432AXSP16	67.3	112.7	83.7	95.9	194.3	68.5	112.4	84	95.8	192.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750C9-525AXSP16	81.5	134.2	100.4	114.5	227.2	82.8	133.5	100.7	114.1	224.4	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C9-532AXSP16	75.6	125.8	93.6	106.9	214.8	76.9	125.3	93.9	106.8	212.2	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750C9-625AXSP16	89.7	146.4	109.9	124.8	244.8	91.3	145.7	110.3	124.5	241.7	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750C9-632AXSP16	84.2	139.4	104	118.5	235.4	85.8	138.6	104.4	118.2	232.4	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K2-425AXSP16	71.2	117.9	88.1	100.5	201.5	72.3	117.3	88.2	100.2	199.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K2-432AXSP16	65.3	109.2	81.2	92.8	188.2	66.4	108.9	81.5	92.7	186.2	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K2-525AXSP16	78.7	129.4	96.8	110.3	218.8	79.8	128.9	97.1	110.1	216.1	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K2-532AXSP16	73	121.6	90.5	103.4	207.6	74.2	121.2	90.7	103.2	204.8	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K2-625AXSP16	86.4	140.9	105.8	120	235.4	87.7	140.2	106.1	119.7	232.1	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K2-632AXSP16	81.3	134.2	100.3	114.2	226.7	82.8	133.6	100.6	113.9	223.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K3-425AXSP16	71.2	117.9	88.1	100.5	201.5	72.3	117.3	88.2	100.2	199.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K3-432AXSP16	65.3	109.2	81.2	92.8	188.2	66.4	108.9	81.5	92.7	186.2	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K3-525AXSP16	78.7	129.4	96.8	110.3	218.8	79.8	128.9	97.1	110.1	216.1	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K3-532AXSP16	73	121.6	90.5	103.4	207.6	74.2	121.2	90.7	103.2	204.8	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K3-625AXSP16	86.4	140.9	105.8	120	235.4	87.7	140.2	106.1	119.7	232.1	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K3-632AXSP16	81.3	134.2	100.3	114.2	226.7	82.8	133.6	100.6	113.9	223.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K4-425AXSP16	71.2	117.9	88.1	100.5	201.5	72.3	117.3	88.2	100.2	199.1	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K4-432AXSP16	65.3	109.2	81.2	92.8	188.2	66.4	108.9	81.5	92.7	186.2	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K4-525AXSP16	78.7	129.4	96.8	110.3	218.8	79.8	128.9	97.1	110.1	216.1	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K4-532AXSP16	73	121.6	90.5	103.4	207.6	74.2	121.2	90.7	103.2	204.8	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K4-625AXSP16	86.4	140.9	105.8	120	235.4	87.7	140.2	106.1	119.7	232.1	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K4-632AXSP16	81.3	134.2	100.3	114.2	226.7	82.8	133.6	100.6	113.9	223.8	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K5-425AXSP16	65.3	109.2	81.2	92.8	188.2	66.4	108.9	81.5	92.7	186.2	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K5-432AXSP16	65.3	109.2	81.2	92.8	188.2	66.4	108.9	81.5	92.7	186.2	146	19.7	2"	117	15.7	1-1/2"	176	27.6	2"
EAW-VD1551ZK750K5-525AXSP16	78.7	129.4	96.8	110.3	218.8	79.8	128.9	97.1	110.1	216.1	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K5-532AXSP16	73	121.6	90.5	103.4	207.6	74.2	121.2	90.7	103.2	204.8	180	20.8	2"	144	13.7	2"	216	29.2	2"
EAW-VD1551ZK750K5-625AXSP16	86.4	140.9	105.8	120	235.4	87.7	140.2	106.1	119.7	232.1	225	22.7	2"	180	14.9	2"	270	25.9	3"
EAW-VD1551ZK750K5-632AXSP16	81.3	134.2	100.3	114.2	226.7	82.8	133.6	100.6	113.9	223.8	225	22.7	2"	180	14.9	2"	270		

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1552PB370C5-625AXSP16	136.6	208.6	161.1	179.8	-	136.4	206.5	159.9	178.4	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370C5-632AXSP16	130.3	200.8	154.4	172.7	-	130.1	198.9	153.2	171.3	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370C8-425AXSP12	109.1	173.5	131.4	148.5	-	109.5	172.6	131.2	147.6	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370C8-425AXSP12	100.8	161.6	121.8	137.9	-	101.2	160.5	121.5	137.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K4-425AXSP12	120.3	189.1	144.1	162.4	-	120.8	188.1	143.8	161.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370C8-532AXSP12	112.6	178.9	135.7	153.2	-	113.1	177.8	135.3	152.5	298	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370C8-625AXSP16	136.6	208.6	161.1	179.8	-	136.4	206.5	159.9	178.4	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370C8-632AXSP16	130.3	200.8	154.4	172.7	-	130.1	198.9	153.2	171.3	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370K2-425AXSP12	105.2	167.1	126.6	142.9	-	105.6	166.1	126.3	142.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K2-432AXSP12	97.3	155.7	117.5	133	-	97.7	154.9	117.2	132.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K2-525AXSP12	115.8	181.9	138.5	156.1	-	116.1	180.9	138.2	155.1	299.9	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370K2-532AXSP12	108.4	172.3	130.7	147.5	289.8	108.9	171.2	130.3	146.7	286.5	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370K2-625AXSP16	131.6	200.6	154.9	173	-	131.2	198.4	153.8	171.5	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370K2-632AXSP16	125.5	193.1	148.4	166.3	-	125.1	191.2	147.4	164.6	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370K4-425AXSP12	105.2	167.1	126.6	142.9	-	105.6	166.1	126.3	142.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K4-432AXSP12	97.3	155.7	117.5	133	-	97.7	154.9	117.2	132.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K4-525AXSP12	115.8	181.9	138.5	156.1	-	116.1	180.9	138.2	155.1	299.9	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370K4-532AXSP12	108.4	172.3	130.7	147.5	289.8	108.9	171.2	130.3	146.7	286.5	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370K4-625AXSP16	131.6	200.6	154.9	173	-	131.2	198.4	153.8	171.5	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370K4-632AXSP16	125.5	193.1	148.4	166.3	-	125.1	191.2	147.4	164.6	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370K5-425AXSP12	105.2	167.1	126.6	142.9	-	105.6	166.1	126.3	142.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K5-432AXSP12	97.3	155.7	117.5	133	-	97.7	154.9	117.2	132.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB370K5-525AXSP12	115.8	181.9	138.5	156.1	-	116.1	180.9	138.2	155.1	299.9	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370K5-532AXSP12	108.4	172.3	130.7	147.5	289.8	108.9	171.2	130.3	146.7	286.5	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB370K5-625AXSP16	131.6	200.6	154.9	173	-	131.2	198.4	153.8	171.5	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB370K5-632AXSP16	125.5	193.1	148.4	166.3	-	125.1	191.2	147.4	164.6	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400B3-425AXSP12	106.2	168.5	127.8	144.3	-	106.5	167.6	127.4	143.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400B3-432AXSP12	98.3	157.3	118.8	134.3	-	98.7	156.6	118.7	133.9	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400B3-525AXSP12	116.6	183.2	139.5	156.9	-	117.1	182.1	139.1	156.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400B3-532AXSP16	113.7	177.5	135.5	152.3	-	113.6	176.1	134.7	151.3	-	135	33	1-1/2"	108	21.8	1-1/2"	162	41.7	2"
EAW-VD1552PB400B3-625AXSP16	131.8	200.9	155.3	173.3	-	131.7	199.1	154.3	172.1	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400B3-632AXSP16	126.2	194.2	149.4	167.2	-	125.9	192.5	148.4	165.9	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400C3-425AXSP12	109.1	173.5	131.4	148.5	-	109.5	172.6	131	147.6	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400C3-432AXSP12	100.8	161.6	121.8	137.9	-	101.2	160.5	121.5	137.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400C3-525AXSP12	120.3	189.1	144.1	162.4	-	120.8	188.1	143.8	161.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400C3-532AXSP12	112.6	178.9	135.7	153.2	-	113.1	177.8	135.3	152.5	298	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400C3-625AXSP16	136.6	208.6	161.1	179.8	-	136.4	206.5	159.9	178.4	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400C3-632AXSP16	130.3	200.8	154.4	172.7	-	130.1	198.9	153.2	171.3	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400C9-425AXSP12	109.1	173.5	131.4	148.5	-	109.5	172.6	131	147.6	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400C9-432AXSP12	100.8	161.6	121.8	137.9	-	101.2	160.5	121.5	137.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400C9-525AXSP12	120.3	189.1	144.1	162.4	-	120.8	188.1	143.8	161.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400C9-532AXSP12	112.6	178.9	135.7	153.2	-	113.1	177.8	135.3	152.5	298	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400C9-625AXSP16	136.6	208.6	161.1	179.8	-	136.4	206.5	159.9	178.4	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400C9-632AXSP16	130.3	200.8	154.4	172.7	-	130.1	198.9	153.2	171.3	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400K3-425AXSP12	105.2	167.1	126.6	142.9	-	105.6	166.1	126.3	142.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400K3-432AXSP12	97.3	155.7	117.5	133	-	97.7	154.9	117.2	132.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400K3-525AXSP12	115.8	181.9	138.5	156.1	-	116.1	180.9	138.2	155.1	299.9	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400K3-532AXSP12	108.4	172.3	130.7	147.5	289.8	108.9	171.2	130.3	146.7	286.5	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400K3-625AXSP16	131.6	200.6	154.9	173	-	131.2	198.4	153.8	171.5	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400K3-632AXSP16	125.5	193.1	148.4	166.3	-	125.1	191.2	147.4	164.6	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400K9-425AXSP12	105.2	167.1	126.6	142.9	-	105.6	166.1	126.3	142.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400K9-432AXSP12	97.3	155.7	117.5	133	-	97.7	154.9	117.2	132.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400K9-525AXSP12	115.8	181.9	138.5	156.1	-	116.1	180.9	138.2	155.1	299.9	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400K9-532AXSP12	108.4	172.3	130.7	147.5	289.8	108.9	171.2	130.3	146.7	286.5	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400K9-625AXSP16	131.6	200.6	154.9	173	-	131.2	198.4	153.8	171.5	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400K9-632AXSP16	125.5	193.1	148.4	166.3	-	125.1	191.2	147.4	164.6	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400R3-425AXSP12	106.9	169.7	128.7	145.3	-	107.2	168.8	128.5	144.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400R3-432AXSP12	99	158.6	119.5	135.4	-	99.3	157.5	119.3	134.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB400R3-525AXSP12	117.6	184.9	140.9	158.6	-	118	183.9	140.5	157.9	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400R3-532AXSP12	110.3	175	132.8	149.9	294.8	110.7	174.2	132.5	149.2	291.2	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB400R3-625AXSP16	133.6	203.7	157.4	175.7	-	133.3	201.9	156.2	174.2	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB400R3-632AXSP16	127.5	186.2	150.8	168.9	-	127.1	194.4	149.8	165.7	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550B3-425AXSP12	115.6	194.3	139.2	157.4	-	116	183.2	139.2	156.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550B3-432AXSP12	106.9	171.7	129.3	146.5	-	107.4	170.8	129.2	146	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550B3-525AXSP12	127.1	200.1	152.4																

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1552PB550C8-532AXSP12	125.6	199.9	151.3	171	-	126.3	198.9	151.2	170.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550C8-625AXSP12	148.3	231	176.6	198.4	-	148.7	229.5	176.3	197.4	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550C8-632AXSP12	140.4	221	168.3	189.4	369.4	141	219.6	167.9	188.8	365.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550C9-425AXSP12	121.4	194	146.7	165.7	-	122	193.1	146.4	164.9	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550C9-432AXSP12	111.8	179.6	135.4	153.4	-	112.4	179	135.1	152.8	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550C9-525AXSP12	134.7	212.4	161.5	182.1	-	135.2	211.5	161.2	181.3	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550C9-532AXSP12	125.6	199.9	151.3	171	-	126.3	198.9	151.2	170.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550C9-625AXSP12	148.3	231	176.6	198.4	-	148.7	229.5	176.3	197.4	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550C9-632AXSP12	140.4	221	168.3	189.4	369.4	141	219.6	167.9	188.8	365.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K2-425AXSP12	116.1	185.2	140.1	158.5	-	116.7	184.4	139.8	157.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K2-432AXSP12	107.3	172.4	129.9	147	-	107.8	171.4	129.6	146.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K2-525AXSP12	128.3	202.1	153.8	173.2	-	128.8	201	153.5	172.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K2-532AXSP12	120.2	190.8	144.7	163.4	-	120.6	189.8	144.3	162.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K2-625AXSP12	140.8	219.2	167.9	188.5	362.3	141.4	217.7	167.5	187.4	358.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K2-632AXSP16	138.8	214.5	164.6	184.6	-	138.6	212.8	163.7	183	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550K3-425AXSP12	116.1	185.2	140.1	158.5	-	116.7	184.4	139.8	157.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K3-432AXSP12	107.3	172.4	129.9	147	-	107.8	171.4	129.6	146.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K3-525AXSP12	128.3	202.1	153.8	173.2	-	128.8	201	153.5	172.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K3-532AXSP12	120.2	190.8	144.7	163.4	-	120.6	189.8	144.3	162.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K3-625AXSP12	140.8	219.2	167.9	188.5	362.3	141.4	217.7	167.5	187.4	358.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K3-632AXSP16	138.8	214.5	164.6	184.6	-	138.6	212.8	163.7	183	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550K4-425AXSP12	116.1	185.2	140.1	158.5	-	116.7	184.4	139.8	157.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K4-432AXSP12	107.3	172.4	129.9	147	-	107.8	171.4	129.6	146.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K4-525AXSP12	128.3	202.1	153.8	173.2	-	128.8	201	153.5	172.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K4-532AXSP12	120.2	190.8	144.7	163.4	-	120.6	189.8	144.3	162.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K4-625AXSP12	140.8	219.2	167.9	188.5	362.3	141.4	217.7	167.5	187.4	358.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K4-632AXSP16	138.8	214.5	164.6	184.6	-	138.6	212.8	163.7	183	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550K5-425AXSP12	116.1	185.2	140.1	158.5	-	116.7	184.4	139.8	157.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K5-432AXSP12	107.3	172.4	129.9	147	-	107.8	171.4	129.6	146.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K5-525AXSP12	128.3	202.1	153.8	173.2	-	128.8	201	153.5	172.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K5-532AXSP12	120.2	190.8	144.7	163.4	-	120.6	189.8	144.3	162.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K5-625AXSP12	140.8	219.2	167.9	188.5	362.3	141.4	217.7	167.5	187.4	358.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K5-632AXSP16	138.8	214.5	164.6	184.6	-	138.6	212.8	163.7	183	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550K8-425AXSP12	116.1	185.2	140.1	158.5	-	116.7	184.4	139.8	157.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K8-432AXSP12	107.3	172.4	129.9	147	-	107.8	171.4	129.6	146.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K8-525AXSP12	128.3	202.1	153.8	173.2	-	128.8	201	153.5	172.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K8-532AXSP12	120.2	190.8	144.7	163.4	-	120.6	189.8	144.3	162.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K8-625AXSP12	140.8	219.2	167.9	188.5	362.3	141.4	217.7	167.5	187.4	358.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K8-632AXSP16	138.8	214.5	164.6	184.6	-	138.6	212.8	163.7	183	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550K9-425AXSP12	116.1	185.2	140.1	158.5	-	116.7	184.4	139.8	157.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K9-432AXSP12	107.3	172.4	129.9	147	-	107.8	171.4	129.6	146.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550K9-525AXSP12	128.3	202.1	153.8	173.2	-	128.8	201	153.5	172.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K9-532AXSP12	120.2	190.8	144.7	163.4	-	120.6	189.8	144.3	162.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550K9-625AXSP12	140.8	219.2	167.9	188.5	362.3	141.4	217.7	167.5	187.4	358.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550K9-632AXSP16	138.8	214.5	164.6	184.6	-	138.6	212.8	163.7	183	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD1552PB550R3-425AXSP12	118.8	189.7	143.4	162.2	-	119.4	188.7	143.2	161.6	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550R3-432AXSP12	109.8	176.3	132.9	150.5	-	110.4	175.5	132.7	150.1	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB550R3-525AXSP12	131.3	207	157.4	177.4	-	131.8	205.9	157.1	176.6	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550R3-532AXSP12	122.9	195.4	148	167.2	-	123.4	194.5	147.7	166.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB550R3-625AXSP12	144.2	224.4	171.8	192.9	371.7	144.7	223.3	171.5	192.1	367.5	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB550R3-632AXSP12	136.6	215.4	164	184.8	359.8	137.2	214.1	163.8	183.9	355.6	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750C2-425AXSP12	128.3	205.6	155	175.4	-	129.1	204.7	155	174.9	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750C2-432AXSP12	118.3	190.6	143.3	162.5	-	119	190	143.4	162	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750C2-525AXSP12	141.8	224.4	170.3	192.1	-	142.7	223.6	170.3	191.7	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750C2-532AXSP12	132.5	211.5	159.9	180.9	-	133.3	210.8	159.8	180.2	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750C2-625AXSP12	156	243.2	186	209	-	156.9	242.2	185.8	208.4	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750C2-632AXSP12	148.2	233.2	177.6	200	-	148.9	232.2	177.4	199.4	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750C3-425AXSP12	128.3	205.6	155	175.4	-	129.1	204.7	155	174.9	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750C3-432AXSP12	118.3	190.6	143.3	162.5	-	119	190	143.4	162	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750C3-525AXSP12	141.8	224.4	170.3	192.1	-	142.7	223.6	170.3	191.7	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750C3-532AXSP12	132.5	211.5	159.9	180.9	-	133.3	210.8	159.8	180.2	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750C3-625AXSP12	156	243.2	186	209	-	156.9	242.2	185.8	208.4	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750C3-632AXSP12	148.2	233.2	177.6	200	-	148.9	232.2	177.4	199.4	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750C4-425AXSP12	128.3	205.6	155	175.4	-	129.1	204.7	155	174.9	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750C4-432AXSP12	118.																		

EAW-VD1552PB750K4-525AXSP12	137.2	216.7	164.7	185.7	-	138	215.8	164.6	185.2	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K4-532AXSP12	128.4	204.4	154.8	174.7	-	129.1	203.7	154.6	174.3	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K4-625AXSP12	150.8	235.1	179.7	201.9	-	151.6	234.1	179.5	201.2	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K4-632AXSP12	143	225.4	171.5	193.4	-	143.8	224.2	171.3	192.6	372.9	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K5-425AXSP12	124.3	198.7	150.1	169.7	-	125	197.8	150	169.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750K5-432AXSP12	114.7	184.5	139	157.4	-	115.4	183.9	138.9	157.1	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750K5-525AXSP12	137.2	216.7	164.7	185.7	-	138	215.8	164.6	185.2	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K5-532AXSP12	128.4	204.4	154.8	174.7	-	129.1	203.7	154.6	174.3	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K5-625AXSP12	150.8	235.1	179.7	201.9	-	151.6	234.1	179.5	201.2	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K5-632AXSP12	143	225.4	171.5	193.4	-	143.8	224.2	171.3	192.6	372.9	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K8-425AXSP12	124.3	198.7	150.1	169.7	-	125	197.8	150	169.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750K8-432AXSP12	114.7	184.5	139	157.4	-	115.4	183.9	138.9	157.1	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750K8-525AXSP12	137.2	216.7	164.7	185.7	-	138	215.8	164.6	185.2	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K8-532AXSP12	128.4	204.4	154.8	174.7	-	129.1	203.7	154.6	174.3	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K8-625AXSP12	150.8	235.1	179.7	201.9	-	151.6	234.1	179.5	201.2	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K8-632AXSP12	143	225.4	171.5	193.4	-	143.8	224.2	171.3	192.6	372.9	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K9-425AXSP12	124.3	198.7	150.1	169.7	-	125	197.8	150	169.2	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750K9-432AXSP12	114.7	184.5	139	157.4	-	115.4	183.9	138.9	157.1	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750K9-525AXSP12	137.2	216.7	164.7	185.7	-	138	215.8	164.6	185.2	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K9-532AXSP12	128.4	204.4	154.8	174.7	-	129.1	203.7	154.6	174.3	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750K9-625AXSP12	150.8	235.1	179.7	201.9	-	151.6	234.1	179.5	201.2	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750K9-632AXSP12	143	225.4	171.5	193.4	-	143.8	224.2	171.3	192.6	372.9	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750R3-425AXSP12	121.6	194.2	146.8	166	-	122.4	193.7	146.8	165.7	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750R3-432AXSP12	112.5	180.9	136.2	154.3	-	113.1	180.3	136.2	153.9	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD1552PB750R3-432AXSP12	134.2	211.9	160.9	181.4	-	134.8	211	160.8	180.8	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750R3-532AXSP12	125.7	200.1	151.5	171.2	-	126.4	199.1	151.3	170.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD1552PB750R3-625AXSP12	147.2	229.3	175.6	197	-	148.2	228.2	175.4	196.6	376.3	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552PB750R3-632AXSP12	139.8	220.4	167.9	189	368.4	140.6	219.3	167.6	188.2	364.4	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD1552P370C2-425AXSP08	123.4	198.6	150.2	169.8	335.5	124.1	196.9	149.7	168.8	330.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P370C2-432AXSP12	119.8	188	143.3	161.3	-	119.3	185.9	142	159.5	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370C2-525AXSP12	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C2-532AXSP12	134.3	208.7	159.8	179.3	-	133.8	206.2	158.4	177.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C2-625AXSP12	157.9	239.7	185.4	206.7	-	156.9	236.6	183.5	204.5	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C2-632AXSP12	149.9	229.7	176.9	197.9	-	149.1	226.8	175.3	195.6	370.2	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C2-425AXSP08	123.4	198.6	150.2	169.8	335.5	124.1	196.9	149.7	168.8	330.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P370C2-432AXSP12	119.8	188	143.3	161.3	-	119.3	185.9	142	159.5	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370C2-525AXSP12	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C2-532AXSP12	134.3	208.7	159.8	179.3	-	133.8	206.2	158.4	177.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C2-625AXSP12	157.9	239.7	185.4	206.7	-	156.9	236.6	183.5	204.5	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C2-632AXSP12	149.9	229.7	176.9	197.9	-	149.1	226.8	175.3	195.6	370.2	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C5-425AXSP08	123.4	198.6	150.2	169.8	335.5	124.1	196.9	149.7	168.8	330.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P370C5-432AXSP12	119.8	188	143.3	161.3	-	119.3	185.9	142	159.5	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370C5-525AXSP12	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C5-532AXSP12	134.3	208.7	159.8	179.3	-	133.8	206.2	158.4	177.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C5-625AXSP12	157.9	239.7	185.4	206.7	-	156.9	236.6	183.5	204.5	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C5-632AXSP12	149.9	229.7	176.9	197.9	-	149.1	226.8	175.3	195.6	370.2	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C8-425AXSP08	123.4	198.6	150.2	169.8	335.5	124.1	196.9	149.7	168.8	330.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P370C8-432AXSP12	119.8	188	143.3	161.3	-	119.3	185.9	142	159.5	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370C8-525AXSP12	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C8-532AXSP12	134.3	208.7	159.8	179.3	-	133.8	206.2	158.4	177.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370C8-625AXSP12	157.9	239.7	185.4	206.7	-	156.9	236.6	183.5	204.5	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370C8-632AXSP12	149.9	229.7	176.9	197.9	-	149.1	226.8	175.3	195.6	370.2	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370K2-425AXSP12	124.9	194.4	148.8	167.1	-	124.4	192.5	147.6	165.3	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370K2-432AXSP12	115.7	181.4	138.2	155.5	-	115.4	179.4	137	154	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370K2-525AXSP12	138.1	212.2	163.2	182.8	-	137.4	209.6	161.7	180.7	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370K2-532AXSP12	129.5	200.8	153.7	172.4	-	128.8	198.4	152.4	170.8	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370K2-625AXSP12	151.4	229.2	177.7	198.1	372.2	150.6	226.2	175.9	195.7	365.8	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370K2-632AXSP12	143.8	220.4	169.8	190	361.2	143.2	217.5	168.3	187.7	354.8	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370K4-425AXSP12	124.9	194.4	148.8	167.1	-	124.4	192.5	147.6	165.3	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370K4-432AXSP12	115.7	181.4	138.2	155.5	-	115.4	179.4	137	154	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD1552P370K4-525AXSP12	138.1	212.2	163.2	182.8	-	137.4	209.6	161.7	180.7	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370K4-532AXSP12	129.5	200.8	153.7	172.4	-	128.8	198.4	152.4	170.8	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD1552P370K4-625AXSP12	151.4	229.2	177.7	198.1	372.2	150.6	226.2	175.9	195.7	365.8	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370K4-632AXSP12	143.8	220.4	169.8	190	361.2	143.2	217.5	168.3	187.7	354.8	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P370K5-425AXSP12	124.9	194.4	148.8	167.1	-	124.4	192.5	14											

EAW-VD15S2PI400K9-432AXSP12	115.7	181.4	138.2	155.5	-	115.4	179.4	137	154	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD15S2PI400K9-525AXSP12	138.1	212.2	163.2	182.8	-	137.4	209.6	161.7	180.7	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI400K9-532AXSP12	129.5	200.8	153.7	172.4	-	128.8	198.4	152.4	170.8	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI400K9-625AXSP12	151.4	229.2	177.7	198.1	372.2	150.6	226.2	175.9	195.7	365.8	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI400K9-632AXSP12	143.8	220.4	169.8	190	361.2	143.2	217.5	168.3	187.7	354.8	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI400R3-425AXSP08	121.2	194.8	147.4	166.6	328.9	122	193.6	147.1	165.8	324.4	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI400R3-432AXSP12	117.9	185.2	141	158.7	-	117.7	183.3	139.8	157.2	-	146	29	2"	117	21.6	1-1/2"	176	40.7	2"
EAW-VD15S2PI400R3-532AXSP12	140.7	216.4	166.4	186.4	-	140.1	213.8	164.9	184.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI400R3-532AXSP12	132	204.9	156.8	176.1	-	131.4	202.6	155.5	174.3	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI400R3-625AXSP12	154.4	233.9	181.3	202.1	-	153.5	230.9	179.5	199.7	373.5	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI400R3-632AXSP12	146.8	224.7	173.4	193.9	368.5	146	222.2	171.7	191.7	362.6	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550B3-425AXSP08	132.8	213.2	161.2	182.2	361.1	133.6	212	160.8	181.2	356.3	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550B3-432AXSP08	122.1	198.5	149.4	169.2	338.2	123.1	197.4	149.2	168.5	333.8	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550B3-525AXSP08	147.3	234.8	178.4	201.1	392.7	148.2	233.2	177.9	200	386.9	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550B3-532AXSP12	144	224.2	171.2	192.4	-	143.3	221.9	170	190.6	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550B3-625AXSP12	168.7	256.9	198.7	221.7	-	168.2	254.1	196.8	219.4	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550B3-632AXSP12	160.4	246.5	189.6	212.4	-	159.8	244	188	210.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C2-425AXSP08	138.9	223.2	168.5	190.6	-	139.7	221.6	168	189.8	373.1	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C2-432AXSP08	127.5	206.9	155.6	176.5	353.2	128.3	205.7	155.4	175.7	348.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C2-432AXSP08	155.2	247.2	187.8	211.9	414.2	156	245.5	187.2	210.6	408.3	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550C2-532AXSP12	150.5	234.8	179.3	201.5	-	149.9	232.2	177.9	199.5	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550C2-625AXSP12	178.5	272.3	210.1	234.8	-	177.6	269	208.1	232.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C3-425AXSP08	168.6	259.6	199.7	223.4	-	167.9	256.8	197.9	221.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C3-425AXSP08	138.9	223.2	168.5	190.6	-	139.7	221.6	168	189.8	373.1	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C3-432AXSP08	127.5	206.9	155.6	176.5	353.2	128.3	205.7	155.4	175.7	348.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C3-525AXSP08	155.2	247.2	187.8	211.9	414.2	156	245.5	187.2	210.6	408.3	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550C3-532AXSP12	150.5	234.8	179.3	201.5	-	149.9	232.2	177.9	199.5	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550C3-625AXSP12	178.5	272.3	210.1	234.8	-	177.6	269	208.1	232.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C3-632AXSP12	168.6	259.6	199.7	223.4	-	167.9	256.8	197.9	221.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C4-425AXSP08	138.9	223.2	168.5	190.6	-	139.7	221.6	168	189.8	373.1	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C4-432AXSP08	127.5	206.9	155.6	176.5	353.2	128.3	205.7	155.4	175.7	348.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C4-525AXSP08	155.2	247.2	187.8	211.9	414.2	156	245.5	187.2	210.6	408.3	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550C4-532AXSP12	150.5	234.8	179.3	201.5	-	149.9	232.2	177.9	199.5	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550C4-625AXSP12	178.5	272.3	210.1	234.8	-	177.6	269	208.1	232.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C4-632AXSP12	168.6	259.6	199.7	223.4	-	167.9	256.8	197.9	221.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C5-425AXSP08	138.9	223.2	168.5	190.6	-	139.7	221.6	168	189.8	373.1	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C5-432AXSP08	127.5	206.9	155.6	176.5	353.2	128.3	205.7	155.4	175.7	348.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C5-525AXSP08	155.2	247.2	187.8	211.9	414.2	156	245.5	187.2	210.6	408.3	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550C5-532AXSP12	150.5	234.8	179.3	201.5	-	149.9	232.2	177.9	199.5	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550C5-625AXSP12	178.5	272.3	210.1	234.8	-	177.6	269	208.1	232.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C5-632AXSP12	168.6	259.6	199.7	223.4	-	167.9	256.8	197.9	221.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C8-425AXSP08	138.9	223.2	168.5	190.6	-	139.7	221.6	168	189.8	373.1	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C8-432AXSP08	127.5	206.9	155.6	176.5	353.2	128.3	205.7	155.4	175.7	348.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C8-525AXSP08	155.2	247.2	187.8	211.9	414.2	156	245.5	187.2	210.6	408.3	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550C8-532AXSP12	150.5	234.8	179.3	201.5	-	149.9	232.2	177.9	199.5	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550C8-625AXSP12	178.5	272.3	210.1	234.8	-	177.6	269	208.1	232.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C8-632AXSP12	168.6	259.6	199.7	223.4	-	167.9	256.8	197.9	221.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550C9-425AXSP08	138.9	223.2	168.5	190.6	-	139.7	221.6	168	189.8	373.1	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C9-432AXSP08	127.5	206.9	155.6	176.5	353.2	128.3	205.7	155.4	175.7	348.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550C9-525AXSP08	155.2	247.2	187.8	211.9	414.2	156	245.5	187.2	210.6	408.3	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550C9-532AXSP12	150.5	234.8	179.3	201.5	-	149.9	232.2	177.9	199.5	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550K2-425AXSP08	133	213.8	161.5	182.8	361.8	134	212.4	161.3	181.8	357	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550K2-432AXSP08	122.4	198.9	149.9	169.8	338.8	123.4	197.7	149.5	168.8	334.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550K2-525AXSP08	147.8	235.6	179	201.8	394.2	148.8	234	178.4	200.7	388.7	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550K2-532AXSP12	144.3	224.7	171.8	193	-	143.8	222.3	170.3	191.2	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550K2-625AXSP12	169.7	258.5	199.7	223.1	-	168.9	255.5	197.9	220.6	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550K2-632AXSP12	161	247.7	190.6	213.1	-	160.3	244.8	188.9	210.8	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550K3-425AXSP08	133	213.8	161.5	182.8	361.8	134	212.4	161.3	181.8	357	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550K3-432AXSP08	122.4	198.9	149.9	169.8	338.8	123.4	197.7	149.5	168.8	334.5	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550K3-525AXSP08	147.8	235.6	179	201.8	394.2	148.8	234	178.4	200.7	388.7	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD15S2PI550K3-532AXSP12	144.3	224.7	171.8	193	-	143.8	222.3	170.3	191.2	-	180	30.1	2"	144	19.8	2"	216	42.2	2"
EAW-VD15S2PI550K3-625AXSP12	169.7	258.5	199.7	223.1	-	168.9	255.5	197.9	220.6	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550K3-632AXSP12	161	247.7	190.6	213.1	-	160.3	244.8	188.9	210.8	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD15S2PI550K4-425AXSP08	133	213.8	161.5	182.8	361.8	134	212.4	161.3	181.8	357	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD15S2PI550K4-432AXSP08	122.4	198.9	149																

EAW-VD1552P750C3-425AXSP08	149	239.3	180.3	204.2	-	150.2	238	180.2	203.4	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C3-432AXSP08	136.8	221.9	166.9	189.2	-	137.8	220.5	166.6	188.3	375	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C3-525AXSP08	166.4	264.8	201	226.9	444.7	167.4	263.4	200.7	225.7	439.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C3-532AXSP08	154.7	249.2	188.5	213	422.1	155.7	247.6	188.1	212	416.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C3-625AXSP12	190.5	291.2	224.6	251.1	-	189.8	288.2	222.9	248.8	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750C3-632AXSP12	180.3	278.4	213.8	239.4	-	179.6	275.5	211.9	237.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750C4-425AXSP08	149	239.3	180.3	204.2	-	150.2	238	180.2	203.4	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C4-432AXSP08	136.8	221.9	166.9	189.2	-	137.8	220.5	166.6	188.3	375	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C4-525AXSP08	166.4	264.8	201	226.9	444.7	167.4	263.4	200.7	225.7	439.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C4-532AXSP08	154.7	249.2	188.5	213	422.1	155.7	247.6	188.1	212	416.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C4-625AXSP12	190.5	291.2	224.6	251.1	-	189.8	288.2	222.9	248.8	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750C4-632AXSP12	180.3	278.4	213.8	239.4	-	179.6	275.5	211.9	237.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750C5-425AXSP08	149	239.3	180.3	204.2	-	150.2	238	180.2	203.4	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C5-432AXSP08	136.8	221.9	166.9	189.2	-	137.8	220.5	166.6	188.3	375	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C5-525AXSP08	166.4	264.8	201	226.9	444.7	167.4	263.4	200.7	225.7	439.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C5-532AXSP08	154.7	249.2	188.5	213	422.1	155.7	247.6	188.1	212	416.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C5-625AXSP12	190.5	291.2	224.6	251.1	-	189.8	288.2	222.9	248.8	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750C5-632AXSP12	180.3	278.4	213.8	239.4	-	179.6	275.5	211.9	237.1	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750C9-425AXSP08	149	239.3	180.3	204.2	-	150.2	238	180.2	203.4	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C9-432AXSP08	136.8	221.9	166.9	189.2	-	137.8	220.5	166.6	188.3	375	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750C9-525AXSP08	166.4	264.8	201	226.9	444.7	167.4	263.4	200.7	225.7	439.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750C9-532AXSP08	154.7	249.2	188.5	213	422.1	155.7	247.6	188.1	212	416.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K2-432AXSP08	132.5	214.9	161.7	183.4	367.5	133.5	214	161.7	182.6	362.7	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K2-525AXSP08	160.4	255.6	193.9	218.9	428.6	161.5	253.7	193.5	217.9	423.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K2-532AXSP08	149.4	240.9	181.9	205.8	407	150.6	239.4	181.8	205.1	401.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K2-625AXSP12	183.6	280.3	216.4	241.9	-	183	277.5	214.8	239.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K2-632AXSP12	174	268.3	206.2	231.2	-	173.5	265.8	204.6	228.9	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K3-425AXSP08	144.2	231.5	174.8	197.8	-	145	230.2	174.5	196.9	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K3-432AXSP08	132.5	214.9	161.7	183.4	367.5	133.5	214	161.7	182.6	362.7	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K3-525AXSP08	160.4	255.6	193.9	218.9	428.6	161.5	253.7	193.5	217.9	423.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K3-532AXSP08	149.4	240.9	181.9	205.8	407	150.6	239.4	181.8	205.1	401.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K3-625AXSP12	183.6	280.3	216.4	241.9	-	183	277.5	214.8	239.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K3-632AXSP12	174	268.3	206.2	231.2	-	173.5	265.8	204.6	228.9	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K4-425AXSP08	144.2	231.5	174.8	197.8	-	145	230.2	174.5	196.9	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K4-432AXSP08	132.5	214.9	161.7	183.4	367.5	133.5	214	161.7	182.6	362.7	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K4-525AXSP08	160.4	255.6	193.9	218.9	428.6	161.5	253.7	193.5	217.9	423.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K4-532AXSP08	149.4	240.9	181.9	205.8	407	150.6	239.4	181.8	205.1	401.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K4-625AXSP12	183.6	280.3	216.4	241.9	-	183	277.5	214.8	239.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K4-632AXSP12	174	268.3	206.2	231.2	-	173.5	265.8	204.6	228.9	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K5-425AXSP08	144.2	231.5	174.8	197.8	-	145	230.2	174.5	196.9	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K5-432AXSP08	132.5	214.9	161.7	183.4	367.5	133.5	214	161.7	182.6	362.7	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K5-525AXSP08	160.4	255.6	193.9	218.9	428.6	161.5	253.7	193.5	217.9	423.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K5-532AXSP08	149.4	240.9	181.9	205.8	407	150.6	239.4	181.8	205.1	401.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K5-625AXSP12	183.6	280.3	216.4	241.9	-	183	277.5	214.8	239.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K5-632AXSP12	174	268.3	206.2	231.2	-	173.5	265.8	204.6	228.9	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K8-425AXSP08	144.2	231.5	174.8	197.8	-	145	230.2	174.5	196.9	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K8-432AXSP08	132.5	214.9	161.7	183.4	367.5	133.5	214	161.7	182.6	362.7	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K8-525AXSP08	160.4	255.6	193.9	218.9	428.6	161.5	253.7	193.5	217.9	423.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K8-532AXSP08	149.4	240.9	181.9	205.8	407	150.6	239.4	181.8	205.1	401.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K8-625AXSP12	183.6	280.3	216.4	241.9	-	183	277.5	214.8	239.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K8-632AXSP12	174	268.3	206.2	231.2	-	173.5	265.8	204.6	228.9	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K9-425AXSP08	144.2	231.5	174.8	197.8	-	145	230.2	174.5	196.9	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K9-432AXSP08	132.5	214.9	161.7	183.4	367.5	133.5	214	161.7	182.6	362.7	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750K9-525AXSP08	160.4	255.6	193.9	218.9	428.6	161.5	253.7	193.5	217.9	423.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K9-532AXSP08	149.4	240.9	181.9	205.8	407	150.6	239.4	181.8	205.1	401.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750K9-625AXSP12	183.6	280.3	216.4	241.9	-	183	277.5	214.8	239.3	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750K9-632AXSP12	174	268.3	206.2	231.2	-	173.5	265.8	204.6	228.9	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750R3-425AXSP08	141	226.4	171.1	193.5	-	142	225.1	170.8	192.7	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750R3-432AXSP08	129.7	210.4	158.5	179.7	359.6	130.8	209.5	158.2	178.9	355.4	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD1552P750R3-525AXSP08	156.8	249.6	189.8	213.8	418.3	157.9	248.1	189.4	212.9	412.9	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750R3-532AXSP08	146.1	235.6	178.1	201.7	398.2	147.5	234.4	177.9	200.6	393.1	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD1552P750R3-625AXSP12	179.4	273.3	211.1	235.9	-	178.5	270.5	209.5	233.7	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552P750R3-632AXSP12	170.4	262.4	201.5	225.8	-	169.8	259.6	199.9	223.6	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD1552PK370C2-425AXSP12	116.7	184.3	140.1	157.7	-	116.7	182.6	139.3	156.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370C2-432AXSP12	107.8	171.4	129.8																

EAW-VD1552PK370K2-632AXSP16	133.8	204.5	157.7	176.3	-	133.2	202.3	156.2	174.5	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK370K4-425AXSP12	112.4	177.1	134.8	152	-	112.4	175.7	134	150.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370K4-432AXSP12	104.1	165.4	125.3	141.3	-	104.2	164	124.5	140.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370K4-525AXSP12	124	193.2	147.8	166	-	124.2	191.6	147	164.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK370K4-532AXSP12	116.3	182.8	139.3	156.8	-	116.4	181.3	138.6	155.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK370K4-625AXSP12	135.7	208.8	161	179.9	342.2	135.6	206.9	159.9	178.3	337	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK370K4-632AXSP16	133.8	204.5	157.7	176.3	-	133.2	202.3	156.2	174.5	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK370K5-425AXSP12	112.4	177.1	134.8	152	-	112.4	175.7	134	150.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370K5-432AXSP12	104.1	165.4	125.3	141.3	-	104.2	164	124.5	140.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370K5-525AXSP12	124	193.2	147.8	166	-	124.2	191.6	147	164.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK370K5-532AXSP12	116.3	182.8	139.3	156.8	-	116.4	181.3	138.6	155.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK370K5-625AXSP12	135.7	208.8	161	179.9	342.2	135.6	206.9	159.9	178.3	337	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK370K5-632AXSP16	133.8	204.5	157.7	176.3	-	133.2	202.3	156.2	174.5	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK370K8-425AXSP12	112.4	177.1	134.8	152	-	112.4	175.7	134	150.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370K8-432AXSP12	104.1	165.4	125.3	141.3	-	104.2	164	124.5	140.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK370K8-525AXSP12	124	193.2	147.8	166	-	124.2	191.6	147	164.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK370K8-532AXSP12	116.3	182.8	139.3	156.8	-	116.4	181.3	138.6	155.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK370K8-625AXSP12	135.7	208.8	161	179.9	342.2	135.6	206.9	159.9	178.3	337	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK370K8-632AXSP16	133.8	204.5	157.7	176.3	-	133.2	202.3	156.2	174.5	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK400B3-425AXSP12	113.8	179.4	136.3	153.7	-	113.9	177.9	135.6	152.5	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400B3-432AXSP12	105.3	167.2	126.8	143	-	105.5	166.1	126	142	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400B3-525AXSP12	125.2	195.2	149.2	167.7	-	125.3	193.6	148.5	166.5	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400B3-532AXSP12	117.6	184.8	140.7	158.6	-	117.7	183.4	140.1	157.4	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400B3-625AXSP12	136.6	210.3	161.9	181.2	344.3	136.7	208.3	161	179.8	339.5	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400B3-632AXSP16	134.9	206.5	159.2	178	-	134.3	204.1	157.8	176.1	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK400C3-425AXSP12	116.7	184.3	140.1	157.7	-	116.7	182.6	139.3	156.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400C3-432AXSP12	107.8	171.4	129.8	146.5	-	107.9	170	129.3	145.5	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400C3-525AXSP12	129	201.1	153.8	172.9	-	129.1	199.4	153.1	171.7	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400C3-532AXSP12	120.8	190	144.7	163	-	120.9	188.4	143.8	161.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400C3-625AXSP12	141.5	217.8	167.7	187.7	357.2	141.4	215.8	166.7	186.2	351.9	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400C3-632AXSP12	134.3	209.1	160.3	180	346.3	134.4	207.3	159.4	178.5	341.4	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400C9-425AXSP12	116.7	184.3	140.1	157.7	-	116.7	182.6	139.3	156.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400C9-432AXSP12	107.8	171.4	129.8	146.5	-	107.9	170	129.3	145.5	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400C9-525AXSP12	129	201.1	153.8	172.9	-	129.1	199.4	153.1	171.7	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400C9-532AXSP12	120.8	190	144.7	163	-	120.9	188.4	143.8	161.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400C9-625AXSP12	141.5	217.8	167.7	187.7	357.2	141.4	215.8	166.7	186.2	351.9	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400C9-632AXSP12	134.3	209.1	160.3	180	346.3	134.4	207.3	159.4	178.5	341.4	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400K3-425AXSP12	112.4	177.1	134.8	152	-	112.4	175.7	134	150.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400K3-432AXSP12	104.1	165.4	125.3	141.3	-	104.2	164	124.5	140.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400K3-525AXSP12	124	193.2	147.8	166	-	124.2	191.6	147	164.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400K3-532AXSP12	116.3	182.8	139.3	156.8	-	116.4	181.3	138.6	155.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400K3-625AXSP12	135.7	208.8	161	179.9	342.2	135.6	206.9	159.9	178.3	337	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400K3-632AXSP16	133.8	204.5	157.7	176.3	-	133.2	202.3	156.2	174.5	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK400K9-425AXSP12	112.4	177.1	134.8	152	-	112.4	175.7	134	150.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400K9-432AXSP12	104.1	165.4	125.3	141.3	-	104.2	164	124.5	140.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400K9-525AXSP12	124	193.2	147.8	166	-	124.2	191.6	147	164.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400K9-532AXSP12	116.3	182.8	139.3	156.8	-	116.4	181.3	138.6	155.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400K9-625AXSP12	135.7	208.8	161	179.9	342.2	135.6	206.9	159.9	178.3	337	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400K9-632AXSP16	133.8	204.5	157.7	176.3	-	133.2	202.3	156.2	174.5	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK400R3-425AXSP12	114.5	180.6	137.1	154.6	-	114.5	179.2	136.6	153.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400R3-432AXSP12	106	168.4	127.4	144	-	106	167	126.9	143.1	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK400R3-525AXSP12	126.2	196.7	150.3	169	-	126.2	195.1	149.6	167.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400R3-532AXSP12	118.4	186.3	141.8	159.7	-	118.6	184.6	141	158.4	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK400R3-625AXSP12	138.1	212.4	163.6	183.1	348.2	138	210.5	162.6	181.6	343	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK400R3-632AXSP16	136.2	208.1	160.4	179.4	-	135.4	206	159	177.7	-	169	33.4	2"	135	25.3	1-1/2"	203	46.8	2"
EAW-VD1552PK508B3-425AXSP12	124.3	196.4	149.1	168.1	-	124.4	195.3	148.6	167.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK508B3-432AXSP12	114.9	182.7	138.3	156.2	-	115	181.5	137.9	155.4	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK508B3-525AXSP12	136.9	214.1	163.4	183.8	-	137.2	212.7	162.9	182.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK508B3-625AXSP12	128.4	202.4	154.1	173.4	-	128.7	201.2	153.5	172.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK508B3-632AXSP12	150.2	231.3	177.9	199.2	-	150.3	229.8	177.2	198.1	375.5	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK508B3-632AXSP12	143	222.5	170.3	191.3	369.6	143.1	220.9	169.6	190.1	364.5	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK508C2-425AXSP12	130.3	206.2	156.5	176.6	-	130.3	204.9	155.8	175.4	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK508C2-432AXSP12	119.9	191.1	144.5	163.4	-	120.1	189.7	144	162.5	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK508C2-525AXSP12	144.6	226.3	172.6	194.4	-	144.6	224.7	172	192.9	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK508C2-532AXSP12	134.9	212.9	161.7	182.4	-	135	211.4	161.1	181.1	-	1								

EAW-VD15S2PK550K2-625AXSP12	151.5	233.7	179.7	201.2	-	151.6	231.9	178.8	199.8	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550K2-632AXSP12	143.7	224.2	171.5	192.7	371.9	-	144	222.4	170.7	191.4	367	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD15S2PK550K3-425AXSP12	124.8	197.2	149.7	168.8	-	124.8	196	149.1	167.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K3-432AXSP12	115.1	183.5	138.6	156.6	-	115.3	182.2	138.2	155.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K3-525AXSP12	137.9	215.6	164.6	185.2	-	137.9	214.1	164	183.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K3-532AXSP12	129.1	203.5	154.6	174.3	-	129.2	202.1	154.1	173.3	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K3-625AXSP12	151.5	233.7	179.7	201.2	-	151.6	231.9	178.8	199.8	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550K3-632AXSP12	143.7	224.2	171.5	192.7	371.9	-	144	222.4	170.7	191.4	367	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD15S2PK550K4-425AXSP12	124.8	197.2	149.7	168.8	-	124.8	196	149.1	167.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K4-432AXSP12	115.1	183.5	138.6	156.6	-	115.3	182.2	138.2	155.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K4-525AXSP12	137.9	215.6	164.6	185.2	-	137.9	214.1	164	183.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K4-532AXSP12	129.1	203.5	154.6	174.3	-	129.2	202.1	154.1	173.3	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K4-625AXSP12	151.5	233.7	179.7	201.2	-	151.6	231.9	178.8	199.8	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550K4-632AXSP12	143.7	224.2	171.5	192.7	371.9	-	144	222.4	170.7	191.4	367	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD15S2PK550K5-425AXSP12	124.8	197.2	149.7	168.8	-	124.8	196	149.1	167.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K5-432AXSP12	115.1	183.5	138.6	156.6	-	115.3	182.2	138.2	155.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K5-525AXSP12	137.9	215.6	164.6	185.2	-	137.9	214.1	164	183.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K5-532AXSP12	129.1	203.5	154.6	174.3	-	129.2	202.1	154.1	173.3	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K5-625AXSP12	151.5	233.7	179.7	201.2	-	151.6	231.9	178.8	199.8	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550K5-632AXSP12	143.7	224.2	171.5	192.7	371.9	-	144	222.4	170.7	191.4	367	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD15S2PK550K8-425AXSP12	124.8	197.2	149.7	168.8	-	124.8	196	149.1	167.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K8-432AXSP12	115.1	183.5	138.6	156.6	-	115.3	182.2	138.2	155.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K8-525AXSP12	137.9	215.6	164.6	185.2	-	137.9	214.1	164	183.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K8-532AXSP12	129.1	203.5	154.6	174.3	-	129.2	202.1	154.1	173.3	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K8-625AXSP12	151.5	233.7	179.7	201.2	-	151.6	231.9	178.8	199.8	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550K8-632AXSP12	143.7	224.2	171.5	192.7	371.9	-	144	222.4	170.7	191.4	367	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD15S2PK550K9-425AXSP12	124.8	197.2	149.7	168.8	-	124.8	196	149.1	167.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K9-432AXSP12	115.1	183.5	138.6	156.6	-	115.3	182.2	138.2	155.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550K9-525AXSP12	137.9	215.6	164.6	185.2	-	137.9	214.1	164	183.8	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K9-532AXSP12	129.1	203.5	154.6	174.3	-	129.2	202.1	154.1	173.3	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550K9-625AXSP12	151.5	233.7	179.7	201.2	-	151.6	231.9	178.8	199.8	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550K9-632AXSP12	143.7	224.2	171.5	192.7	371.9	-	144	222.4	170.7	191.4	367	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD15S2PK550R3-425AXSP12	127.9	202.2	153.5	173.2	-	128	201	153	172.1	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550R3-432AXSP12	117.9	188	142.1	160.6	-	118.1	186.8	141.7	159.8	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK550R3-525AXSP12	141.3	220.9	168.7	189.6	-	141.4	219.4	167.9	188.5	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550R3-532AXSP12	132.2	208.8	158.4	178.7	-	132.5	207.2	157.8	177.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK550R3-625AXSP12	155.4	239.7	184.1	206.3	-	155.4	237.9	183.3	204.9	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK550R3-632AXSP12	147.5	229.9	175.8	197.5	-	147.7	228.2	175	196.3	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C2-425AXSP08	130.1	214.4	160.4	182.2	368.6	-	132.1	213.9	161.2	182.5	365	225	20.2	2"	180	13.3	2"	270	22.8	3"
EAW-VD15S2PK750C2-432AXSP12	127.5	203.7	153.7	174	-	127.6	202.2	153.3	172.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK750C2-525AXSP12	153.2	240.5	183.4	206.3	-	153.5	239.2	182.7	205.1	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C2-532AXSP12	143.1	226.4	171.7	193.7	-	143.3	224.9	171.2	192.9	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C2-625AXSP12	168.8	261.3	200.5	224.8	-	169.1	259.7	199.6	223.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C2-632AXSP12	160.1	250.2	191	214.9	-	160.2	248.3	190.1	213.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C3-425AXSP08	130.1	214.4	160.4	182.2	368.6	-	132.1	213.9	161.2	182.5	365	225	20.2	2"	180	13.3	2"	270	22.8	3"
EAW-VD15S2PK750C3-432AXSP12	127.5	203.7	153.7	174	-	127.6	202.2	153.3	172.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK750C3-525AXSP12	153.2	240.5	183.4	206.3	-	153.5	239.2	182.7	205.1	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C3-532AXSP12	143.1	226.4	171.7	193.7	-	143.3	224.9	171.2	192.9	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C3-625AXSP12	168.8	261.3	200.5	224.8	-	169.1	259.7	199.6	223.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C3-632AXSP12	160.1	250.2	191	214.9	-	160.2	248.3	190.1	213.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C4-425AXSP08	130.1	214.4	160.4	182.2	368.6	-	132.1	213.9	161.2	182.5	365	225	20.2	2"	180	13.3	2"	270	22.8	3"
EAW-VD15S2PK750C4-432AXSP12	127.5	203.7	153.7	174	-	127.6	202.2	153.3	172.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK750C4-525AXSP12	153.2	240.5	183.4	206.3	-	153.5	239.2	182.7	205.1	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C4-532AXSP12	143.1	226.4	171.7	193.7	-	143.3	224.9	171.2	192.9	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C4-625AXSP12	168.8	261.3	200.5	224.8	-	169.1	259.7	199.6	223.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C4-632AXSP12	160.1	250.2	191	214.9	-	160.2	248.3	190.1	213.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C5-425AXSP08	130.1	214.4	160.4	182.2	368.6	-	132.1	213.9	161.2	182.5	365	225	20.2	2"	180	13.3	2"	270	22.8	3"
EAW-VD15S2PK750C5-432AXSP12	127.5	203.7	153.7	174	-	127.6	202.2	153.3	172.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK750C5-525AXSP12	153.2	240.5	183.4	206.3	-	153.5	239.2	182.7	205.1	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C5-532AXSP12	143.1	226.4	171.7	193.7	-	143.3	224.9	171.2	192.9	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK750C5-625AXSP12	168.8	261.3	200.5	224.8	-	169.1	259.7	199.6	223.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C5-632AXSP12	160.1	250.2	191	214.9	-	160.2	248.3	190.1	213.4	-	225	27.9	2"	180	18.4	2"	270	33.5	3"	
EAW-VD15S2PK750C8-425AXSP08	130.1	214.4	160.4	182.2	368.6	-	132.1	213.9	161.2	182.5	365	225	20.2	2"	180	13.3	2"	270	22.8	3"
EAW-VD15S2PK750C8-432AXSP12	127.5	203.7	153.7	174	-	127.6	202.2	153.3	172.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"	
EAW-VD15S2PK750C8-525AXSP12	153.2	240.5	183.4	206.3	-	153.5	239.2	182.7	205.1	-	180	26.1	2"	144	17.2	2"	216	36.7	2"	
EAW-VD15S2PK75																				

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1552PK750K8-532AXSP12	138.4	218.8	166.2	187.4	-	138.9	217.4	165.5	186.4	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK750K8-625AXSP12	162.7	251.8	193.2	216.6	-	163.2	249.8	192.5	215.3	-	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK750K8-632AXSP12	154.7	241.3	184.4	207.1	-	154.8	239.7	183.6	206	-	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK750K9-425AXSP08	125.8	207.1	155.3	176.6	356	127.7	207	155.9	176.4	352.6	225	20.2	2"	180	13.3	2"	270	22.8	3"
EAW-VD1552PK750K9-432AXSP12	123.5	197.1	149	168.5	-	123.8	196	148.5	167.7	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK750K9-525AXSP12	148	231.9	176.8	199.1	-	148.2	230.6	176.4	197.9	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK750K9-532AXSP12	138.4	218.8	166.2	187.4	-	138.9	217.4	165.5	186.4	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK750K9-625AXSP12	162.7	251.8	193.2	216.6	-	163.2	249.8	192.5	215.3	-	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK750K9-632AXSP12	154.7	241.3	184.4	207.1	-	154.8	239.7	183.6	206	-	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK750R3-425AXSP12	131.1	207.7	157.5	177.8	-	131.5	206.7	157.2	176.9	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK750R3-432AXSP12	121.1	193.3	146	165	-	121.3	191.9	145.6	164.3	-	146	25	2"	117	19	1-1/2"	176	35.1	2"
EAW-VD1552PK750R3-525AXSP12	144.8	226.7	173	194.5	-	145.1	225.4	172.3	193.6	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK750R3-532AXSP12	135.6	214.2	162.6	183.5	-	135.8	212.8	162.1	182.5	-	180	26.1	2"	144	17.2	2"	216	36.7	2"
EAW-VD1552PK750R3-625AXSP12	159.1	245.6	188.8	211.6	-	159.2	244	187.8	210.1	-	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552PK750R3-632AXSP12	151.2	235.9	180.2	202.6	-	151.5	234	179.6	201.1	-	225	27.9	2"	180	18.4	2"	270	33.5	3"
EAW-VD1552ZB370C2-425AXSP12	127.6	202.1	153.6	173.2	-	127.9	200.3	152.6	171.6	334.5	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370C2-432AXSP16	119.6	187.8	143.1	161.1	-	119.1	185.7	141.8	159.5	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370C2-525AXSP16	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C2-532AXSP16	134.4	208.6	159.7	179.2	-	133.7	206.4	158.2	177.2	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C2-625AXSP16	158	239.9	185.6	207.2	-	157	236.8	183.6	204.6	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C2-632AXSP16	150	229.8	176.9	198	-	149.1	226.9	175.4	195.6	370.5	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C4-425AXSP12	127.6	202.1	153.6	173.2	-	127.9	200.3	152.6	171.6	334.5	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370C4-432AXSP16	119.6	187.8	143.1	161.1	-	119.1	185.7	141.8	159.5	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370C4-525AXSP16	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C4-532AXSP16	134.4	208.6	159.7	179.2	-	133.7	206.4	158.2	177.2	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C4-625AXSP16	158	239.9	185.6	207.2	-	157	236.8	183.6	204.6	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C4-632AXSP16	150	229.8	176.9	198	-	149.1	226.9	175.4	195.6	370.5	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C5-425AXSP12	127.6	202.1	153.6	173.2	-	127.9	200.3	152.6	171.6	334.5	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370C5-432AXSP16	119.6	187.8	143.1	161.1	-	119.1	185.7	141.8	159.5	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370C5-525AXSP16	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C5-532AXSP16	134.4	208.6	159.7	179.2	-	133.7	206.4	158.2	177.2	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C5-625AXSP16	158	239.9	185.6	207.2	-	157	236.8	183.6	204.6	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C5-632AXSP16	150	229.8	176.9	198	-	149.1	226.9	175.4	195.6	370.5	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C8-425AXSP12	127.6	202.1	153.6	173.2	-	127.9	200.3	152.6	171.6	334.5	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370C8-432AXSP16	119.6	187.8	143.1	161.1	-	119.1	185.7	141.8	159.5	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370C8-432AXSP16	119.6	187.8	143.1	161.1	-	119.1	185.7	141.8	159.5	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370C8-525AXSP16	143.5	221	170	190.2	-	142.9	218.6	168.4	188.3	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C8-532AXSP16	134.4	208.6	159.7	179.2	-	133.7	206.4	158.2	177.2	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370C8-625AXSP16	158	239.9	185.6	207.2	-	157	236.8	183.6	204.6	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370C8-632AXSP16	150	229.8	176.9	198	-	149.1	226.9	175.4	195.6	370.5	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K2-425AXSP12	122.7	194.3	147.7	166.5	326	123	192.7	147	165.2	321.3	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370K2-432AXSP16	115.7	181.2	138	155.4	-	115.2	179.3	137.1	153.9	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370K2-525AXSP16	138.1	212.3	163.2	182.8	-	137.4	209.7	161.7	180.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K2-532AXSP16	129.4	200.8	153.7	172.4	-	128.8	198.4	152.3	170.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K2-625AXSP16	151.5	229.4	177.9	198.3	372.6	150.5	226.5	176	195.8	366.2	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K2-632AXSP16	143.8	220.5	169.9	190	361.4	143.2	217.6	168.4	187.7	355	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K4-425AXSP12	122.7	194.3	147.7	166.5	326	123	192.7	147	165.2	321.3	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370K4-432AXSP16	115.7	181.2	138	155.4	-	115.2	179.3	137.1	153.9	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370K4-525AXSP16	138.1	212.3	163.2	182.8	-	137.4	209.7	161.7	180.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K4-532AXSP16	129.4	200.8	153.7	172.4	-	128.8	198.4	152.3	170.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K4-625AXSP16	151.5	229.4	177.9	198.3	372.6	150.5	226.5	176	195.8	366.2	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K4-632AXSP16	143.8	220.5	169.9	190	361.4	143.2	217.6	168.4	187.7	355	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K5-425AXSP12	122.7	194.3	147.7	166.5	326	123	192.7	147	165.2	321.3	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370K5-432AXSP16	115.7	181.2	138	155.4	-	115.2	179.3	137.1	153.9	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370K5-525AXSP16	138.1	212.3	163.2	182.8	-	137.4	209.7	161.7	180.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K5-532AXSP16	129.4	200.8	153.7	172.4	-	128.8	198.4	152.3	170.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K5-625AXSP16	151.5	229.4	177.9	198.3	372.6	150.5	226.5	176	195.8	366.2	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K5-632AXSP16	143.8	220.5	169.9	190	361.4	143.2	217.6	168.4	187.7	355	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K8-425AXSP12	122.7	194.3	147.7	166.5	326	123	192.7	147	165.2	321.3	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB370K8-432AXSP16	115.7	181.2	138	155.4	-	115.2	179.3	137.1	153.9	-	146	30.2	2"	117	22.6	1-1/2"	176	42.4	2"
EAW-VD1552ZB370K8-525AXSP16	138.1	212.3	163.2	182.8	-	137.4	209.7	161.7	180.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K8-532AXSP16	129.4	200.8	153.7	172.4	-	128.8	198.4	152.3	170.7	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD1552ZB370K8-625AXSP16	151.5	229.4	177.9	198.3	372.6	150.5	226.5	176	195.8	366.2	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB370K8-632AXSP16	143.8	220.5	169.9	190	361.4	143.2	217.6	168.4	187.7	355	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB400B3-425AXSP12	124.6	19																	

EAW-VD15S2ZB550B3-525AXSP12	150.4	236.3	180.4	202.7	393.6	150.8	234.3	179.6	201.3	387.8	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550B3-532AXSP16	144	223.9	171.2	192.4	-	143.5	221.9	170	190.5	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD15S2ZB550B3-632AXSP16	169	257.4	199	222	-	168.5	254.5	197.1	219.8	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550B3-632AXSP16	160.5	246.7	190	212.5	-	159.9	244.2	188.4	210.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C2-425AXSP12	143.2	227.4	172.3	194.7	-	143.4	225.3	171.6	193.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C2-432AXSP12	131.8	210.7	159.4	180.2	-	132.1	209.3	158.5	179	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C2-525AXSP12	158.2	248.7	189.6	213.5	-	158.5	246.6	188.6	211.9	409.1	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C2-532AXSP12	147.2	233.6	177.7	200.1	393	147.4	231.7	176.6	198.7	387.3	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C2-625AXSP16	178.6	272.6	210.2	235	-	177.7	269.2	208.5	232.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C2-632AXSP16	168.6	259.7	199.8	223.5	-	167.9	256.9	197.9	221.4	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C3-425AXSP12	143.2	227.4	172.3	194.7	-	143.4	225.3	171.6	193.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C3-432AXSP12	131.8	210.7	159.4	180.2	-	132.1	209.3	158.5	179	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C3-532AXSP12	147.2	233.6	177.7	200.1	393	147.4	231.7	176.6	198.7	387.3	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C3-632AXSP16	178.6	272.6	210.2	235	-	177.7	269.2	208.5	232.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C3-632AXSP16	168.6	259.7	199.8	223.5	-	167.9	256.9	197.9	221.4	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C4-425AXSP12	143.2	227.4	172.3	194.7	-	143.4	225.3	171.6	193.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C4-432AXSP12	131.8	210.7	159.4	180.2	-	132.1	209.3	158.5	179	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C4-525AXSP12	158.2	248.7	189.6	213.5	-	158.5	246.6	188.6	211.9	409.1	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C4-532AXSP12	147.2	233.6	177.7	200.1	393	147.4	231.7	176.6	198.7	387.3	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C4-625AXSP16	178.6	272.6	210.2	235	-	177.7	269.2	208.5	232.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C4-632AXSP16	168.6	259.7	199.8	223.5	-	167.9	256.9	197.9	221.4	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C5-425AXSP12	143.2	227.4	172.3	194.7	-	143.4	225.3	171.6	193.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C5-432AXSP12	131.8	210.7	159.4	180.2	-	132.1	209.3	158.5	179	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C5-525AXSP12	158.2	248.7	189.6	213.5	-	158.5	246.6	188.6	211.9	409.1	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C5-532AXSP12	147.2	233.6	177.7	200.1	393	147.4	231.7	176.6	198.7	387.3	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C5-625AXSP16	178.6	272.6	210.2	235	-	177.7	269.2	208.5	232.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C5-632AXSP16	168.6	259.7	199.8	223.5	-	167.9	256.9	197.9	221.4	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C8-425AXSP12	143.2	227.4	172.3	194.7	-	143.4	225.3	171.6	193.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C8-432AXSP12	131.8	210.7	159.4	180.2	-	132.1	209.3	158.5	179	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C8-525AXSP12	158.2	248.7	189.6	213.5	-	158.5	246.6	188.6	211.9	409.1	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C8-532AXSP12	147.2	233.6	177.7	200.1	393	147.4	231.7	176.6	198.7	387.3	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C8-625AXSP16	178.6	272.6	210.2	235	-	177.7	269.2	208.5	232.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C8-632AXSP16	168.6	259.7	199.8	223.5	-	167.9	256.9	197.9	221.4	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C9-425AXSP12	143.2	227.4	172.3	194.7	-	143.4	225.3	171.6	193.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C9-432AXSP12	131.8	210.7	159.4	180.2	-	132.1	209.3	158.5	179	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550C9-525AXSP12	158.2	248.7	189.6	213.5	-	158.5	246.6	188.6	211.9	409.1	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C9-532AXSP12	147.2	233.6	177.7	200.1	393	147.4	231.7	176.6	198.7	387.3	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550C9-625AXSP16	178.6	272.6	210.2	235	-	177.7	269.2	208.5	232.3	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550C9-632AXSP16	168.6	259.7	199.8	223.5	-	167.9	256.9	197.9	221.4	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K2-425AXSP12	137.4	217.9	165.1	186.4	-	137.8	215.9	164.5	185	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K2-432AXSP12	126.7	202.5	153.2	173.1	-	127.1	201.3	152.7	172	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K2-525AXSP12	150.9	237.1	181	203.7	395	151.2	235.1	180.1	201.9	389	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550K2-532AXSP16	144.2	224.7	171.8	193	-	143.7	222.3	170.2	191.1	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD15S2ZB550K2-625AXSP16	169.9	258.9	199.9	223.4	-	169.1	255.8	198.1	220.9	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K2-632AXSP16	161	247.9	190.7	213.2	-	160.3	244.9	188.9	211.2	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K3-425AXSP12	137.4	217.9	165.1	186.4	-	137.8	215.9	164.5	185	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K3-432AXSP12	126.7	202.5	153.2	173.1	-	127.1	201.3	152.7	172	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K3-525AXSP12	150.9	237.1	181	203.7	395	151.2	235.1	180.1	201.9	389	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550K3-532AXSP16	144.2	224.7	171.8	193	-	143.7	222.3	170.2	191.1	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD15S2ZB550K3-625AXSP16	169.9	258.9	199.9	223.4	-	169.1	255.8	198.1	220.9	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K3-632AXSP16	161	247.9	190.7	213.2	-	160.3	244.9	188.9	211.2	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K4-425AXSP12	137.4	217.9	165.1	186.4	-	137.8	215.9	164.5	185	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K4-432AXSP12	126.7	202.5	153.2	173.1	-	127.1	201.3	152.7	172	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K4-525AXSP12	150.9	237.1	181	203.7	395	151.2	235.1	180.1	201.9	389	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550K4-532AXSP16	144.2	224.7	171.8	193	-	143.7	222.3	170.2	191.1	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD15S2ZB550K4-625AXSP16	169.9	258.9	199.9	223.4	-	169.1	255.8	198.1	220.9	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K4-632AXSP16	161	247.9	190.7	213.2	-	160.3	244.9	188.9	211.2	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K5-425AXSP12	137.4	217.9	165.1	186.4	-	137.8	215.9	164.5	185	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K5-432AXSP12	126.7	202.5	153.2	173.1	-	127.1	201.3	152.7	172	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K5-525AXSP12	150.9	237.1	181	203.7	395	151.2	235.1	180.1	201.9	389	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD15S2ZB550K5-532AXSP16	144.2	224.7	171.8	193	-	143.7	222.3	170.2	191.1	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD15S2ZB550K5-625AXSP16	169.9	258.9	199.9	223.4	-	169.1	255.8	198.1	220.9	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K5-632AXSP16	161	247.9	190.7	213.2	-	160.3	244.9	188.9	211.2	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD15S2ZB550K8-425AXSP12	137.4	217.9	165.1	186.4	-	137.8	215.9	164.5	185	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K8-432AXSP12	126.7	202.5	153.2	173.1	-	127.1	201.3	152.7	172	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD15S2ZB550K8-525AXSP12	150.9	237.1</																	

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1552ZB750C5-432AXSP12	141.2	226.2	170.7	193	-	141.6	224.7	170.1	192.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750C5-525AXSP12	169.5	266.6	203	228.5	-	169.9	264.7	202.3	227.2	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750C5-532AXSP12	157.9	250.8	190.1	214.4	-	158.5	248.8	189.4	213.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750C5-625AXSP16	190.7	291.8	224.9	251.6	-	190.1	288.7	223.1	249.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750C5-632AXSP12	174.3	274.5	209.4	235.7	457.7	174.8	272.4	208.5	234.2	451.7	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750C8-425AXSP12	153.3	244	184.6	208.5	-	153.7	242.2	184	207.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750C8-432AXSP12	141.2	226.2	170.7	193	-	141.6	224.7	170.1	192.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750C8-525AXSP12	169.5	266.6	203	228.5	-	169.9	264.7	202.3	227.2	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750C8-532AXSP12	157.9	250.8	190.1	214.4	-	158.5	248.8	189.4	213.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750C8-625AXSP16	190.7	291.8	224.9	251.6	-	190.1	288.7	223.1	249.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750C8-632AXSP12	174.3	274.5	209.4	235.7	457.7	174.8	272.4	208.5	234.2	451.7	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750C9-425AXSP12	153.3	244	184.6	208.5	-	153.7	242.2	184	207.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750C9-432AXSP12	141.2	226.2	170.7	193	-	141.6	224.7	170.1	192.1	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750C9-525AXSP12	169.5	266.6	203	228.5	-	169.9	264.7	202.3	227.2	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750C9-532AXSP12	157.9	250.8	190.1	214.4	-	158.5	248.8	189.4	213.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750C9-625AXSP16	190.7	291.8	224.9	251.6	-	190.1	288.7	223.1	249.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750C9-632AXSP12	174.3	274.5	209.4	235.7	457.7	174.8	272.4	208.5	234.2	451.7	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K2-425AXSP12	148.3	235.6	178.5	201.9	-	148.7	234.2	177.9	200.6	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K2-432AXSP12	137.1	219	165.3	187.1	-	137.3	217.6	165	186.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K2-525AXSP12	163.6	257.2	195.9	220.7	-	164.2	255.4	195.1	219.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K2-532AXSP12	152.7	242.1	183.8	207.5	407.8	153	240.6	183.4	206.1	402.6	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K2-625AXSP12	177.9	276.9	212.2	238.1	456.6	178.2	274.9	211.6	236.6	450.4	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K2-632AXSP16	174.2	268.6	206.4	231.4	-	173.6	265.7	204.8	229.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750K3-425AXSP12	148.3	235.6	178.5	201.9	-	148.7	234.2	177.9	200.6	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K3-432AXSP12	137.1	219	165.3	187.1	-	137.3	217.6	165	186.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K3-525AXSP12	163.6	257.2	195.9	220.7	-	164.2	255.4	195.1	219.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K3-532AXSP12	152.7	242.1	183.8	207.5	407.8	153	240.6	183.4	206.1	402.6	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K3-625AXSP12	177.9	276.9	212.2	238.1	456.6	178.2	274.9	211.6	236.6	450.4	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K3-632AXSP16	174.2	268.6	206.4	231.4	-	173.6	265.7	204.8	229.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750K4-425AXSP12	148.3	235.6	178.5	201.9	-	148.7	234.2	177.9	200.6	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K4-432AXSP12	137.1	219	165.3	187.1	-	137.3	217.6	165	186.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K4-525AXSP12	163.6	257.2	195.9	220.7	-	164.2	255.4	195.1	219.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K4-532AXSP12	152.7	242.1	183.8	207.5	407.8	153	240.6	183.4	206.1	402.6	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K4-625AXSP12	177.9	276.9	212.2	238.1	456.6	178.2	274.9	211.6	236.6	450.4	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K4-632AXSP16	174.2	268.6	206.4	231.4	-	173.6	265.7	204.8	229.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750K5-425AXSP12	148.3	235.6	178.5	201.9	-	148.7	234.2	177.9	200.6	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K5-432AXSP12	137.1	219	165.3	187.1	-	137.3	217.6	165	186.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K5-525AXSP12	163.6	257.2	195.9	220.7	-	164.2	255.4	195.1	219.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K5-532AXSP12	152.7	242.1	183.8	207.5	407.8	153	240.6	183.4	206.1	402.6	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K5-625AXSP12	177.9	276.9	212.2	238.1	456.6	178.2	274.9	211.6	236.6	450.4	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K5-632AXSP16	174.2	268.6	206.4	231.4	-	173.6	265.7	204.8	229.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750K8-425AXSP12	148.3	235.6	178.5	201.9	-	148.7	234.2	177.9	200.6	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K8-432AXSP12	137.1	219	165.3	187.1	-	137.3	217.6	165	186.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K8-525AXSP12	163.6	257.2	195.9	220.7	-	164.2	255.4	195.1	219.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K8-532AXSP12	152.7	242.1	183.8	207.5	407.8	153	240.6	183.4	206.1	402.6	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K8-625AXSP12	177.9	276.9	212.2	238.1	456.6	178.2	274.9	211.6	236.6	450.4	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K8-632AXSP16	174.2	268.6	206.4	231.4	-	173.6	265.7	204.8	229.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750K9-425AXSP12	148.3	235.6	178.5	201.9	-	148.7	234.2	177.9	200.6	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K9-432AXSP12	137.1	219	165.3	187.1	-	137.3	217.6	165	186.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750K9-525AXSP12	163.6	257.2	195.9	220.7	-	164.2	255.4	195.1	219.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K9-532AXSP12	152.7	242.1	183.8	207.5	407.8	153	240.6	183.4	206.1	402.6	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750K9-625AXSP12	177.9	276.9	212.2	238.1	456.6	178.2	274.9	211.6	236.6	450.4	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD1552ZB750K9-632AXSP16	174.2	268.6	206.4	231.4	-	173.6	265.7	204.8	229.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750R3-425AXSP12	145.5	230.8	175	197.5	-	145.9	229	174.4	196.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750R3-432AXSP12	134.3	214.8	162.1	183.3	-	134.7	213.4	161.7	182.4	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD1552ZB750R3-525AXSP12	160	251.2	191.7	215.6	-	160.5	249.4	191	214.2	413.9	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750R3-532AXSP12	149.2	237.1	179.9	203	399	149.8	235.2	179.4	201.6	393.4	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD1552ZB750R3-625AXSP16	179.4	273.9	211.5	236.4	-	178.8	271.1	209.9	234.1	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZB750R3-632AXSP16	170.5	262.7	201.7	226	-	169.7	259.8	200.1	223.8	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD1552ZK017G7-425AXSP08	179.1	295.1	220.7	251.2	507.9	181.5	293.9	220.8	250.6	502	304	17.1	3"	244	11.3	3"	365	24	3"
EAW-VD1552ZK017G7-432AXSP08	162.7	270.8	202.3	230.4	469.5	165.2	270.3	202.6	230.1	463.8	304	17.1	3"	244	11.3	3"	365	24	3"
EAW-VD1552ZK017G7-525AXSP12	161.2	339.7	258.9	291.3	-	216.1	336.4	257.3	288.9	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK017G7-532AXSP12	199.7	316.5	240.1	270.8	-	199.7	313.7	238.5	268.8	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK017G7-625AXSP12	239.3	371.1	284.3	319.1	-	239	367.2	282.6	316	-	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK017G7-632AXSP12</																			

EAW-VD1552ZK370K5-425AXSP12	130.5	204.6	156	175.6	-	130.4	202.3	154.8	173.8	335.6	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK370K5-432AXSP12	120.7	190.9	145.2	163.7	321.1	120.6	189.2	144.2	162.2	315.7	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK370K5-525AXSP12	142.9	222.1	170.4	191	365.8	142.7	219.4	169	189.1	359.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK370K5-532AXSP16	136.8	210.8	161.8	181.3	-	135.7	208	160.1	179.1	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK370K5-625AXSP16	159.8	240.5	187	208.1	-	158.6	237.2	184.6	205.3	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK370K5-632AXSP16	152.1	231.2	178.7	199.5	-	151	227.9	176.7	196.9	370	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK370K8-425AXSP12	130.5	204.6	156	175.6	-	130.4	202.3	154.8	173.8	335.6	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK370K8-432AXSP12	120.7	190.9	145.2	163.7	321.1	120.6	189.2	144.2	162.2	315.7	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK370K8-525AXSP12	142.9	222.1	170.4	191	365.8	142.7	219.4	169	189.1	359.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK370K8-532AXSP16	136.8	210.8	161.8	181.3	-	135.7	208	160.1	179.1	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK370K8-625AXSP16	159.8	240.5	187	208.1	-	158.6	237.2	184.6	205.3	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK370K8-632AXSP16	152.1	231.2	178.7	199.5	-	151	227.9	176.7	196.9	370	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400B3-425AXSP12	132.3	207.3	158.2	177.9	-	132.3	205.3	157	176.4	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400B3-432AXSP12	122.3	193.5	147.1	165.9	325.3	122.3	191.5	146.1	164.4	320.3	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400B3-525AXSP12	144.9	225	172.8	193.7	371.2	144.7	222.6	171.5	191.6	364.9	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK400B3-532AXSP16	138.5	213.6	164.1	183.9	-	137.6	210.9	162.5	181.7	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK400B3-625AXSP16	162	244.3	189.7	211.3	-	160.8	240.6	187.5	208.2	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400B3-632AXSP16	154.2	234.5	181.3	202.4	-	152.9	231.3	179.2	199.7	375.5	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400C3-425AXSP12	135.4	212.4	162	182.2	-	135.3	210	160.7	180.3	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400C3-432AXSP12	125.1	197.9	150.3	169.6	332.8	124.8	195.8	149.3	168	327.7	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400C3-525AXSP12	148.9	231.1	177.4	198.9	382	148.7	228.6	175.9	196.9	375.4	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK400C3-532AXSP16	141.9	219	168.1	188.1	-	140.9	216	166.1	185.8	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK400C3-625AXSP16	166.7	251.5	195.1	217.4	-	165.4	247.6	192.9	214.3	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400C3-632AXSP16	158.3	240.9	186.1	207.8	-	156.9	237.4	183.9	205	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400C9-425AXSP12	135.4	212.4	162	182.2	-	135.3	210	160.7	180.3	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400C9-432AXSP12	125.1	197.9	150.3	169.6	332.8	124.8	195.8	149.3	168	327.7	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400C9-525AXSP12	148.9	231.1	177.4	198.9	382	148.7	228.6	175.9	196.9	375.4	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK400C9-532AXSP16	141.9	219	168.1	188.1	-	140.9	216	166.1	185.8	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK400C9-625AXSP16	166.7	251.5	195.1	217.4	-	165.4	247.6	192.9	214.3	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400C9-632AXSP16	158.3	240.9	186.1	207.8	-	156.9	237.4	183.9	205	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400K3-425AXSP12	130.5	204.6	156	175.6	-	130.4	202.3	154.8	173.8	335.6	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400K3-432AXSP12	120.7	190.9	145.2	163.7	321.1	120.6	189.2	144.2	162.2	315.7	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400K3-525AXSP12	142.9	222.1	170.4	191	365.8	142.7	219.4	169	189.1	359.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK400K3-532AXSP16	136.8	210.8	161.8	181.3	-	135.7	208	160.1	179.1	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK400K3-625AXSP16	159.8	240.5	187	208.1	-	158.6	237.2	184.6	205.3	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400K3-632AXSP16	152.1	231.2	178.7	199.5	-	151	227.9	176.7	196.9	370	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400K9-425AXSP12	130.5	204.6	156	175.6	-	130.4	202.3	154.8	173.8	335.6	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400K9-432AXSP12	120.7	190.9	145.2	163.7	321.1	120.6	189.2	144.2	162.2	315.7	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400K9-525AXSP12	142.9	222.1	170.4	191	365.8	142.7	219.4	169	189.1	359.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK400K9-532AXSP16	136.8	210.8	161.8	181.3	-	135.7	208	160.1	179.1	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK400K9-625AXSP16	159.8	240.5	187	208.1	-	158.6	237.2	184.6	205.3	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400K9-632AXSP16	152.1	231.2	178.7	199.5	-	151	227.9	176.7	196.9	370	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400R3-425AXSP12	133.4	208.8	159.3	179.4	-	133.2	206.8	158.1	177.6	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400R3-432AXSP12	123.3	195.2	148.3	167.3	328.1	123.3	193.2	147.4	165.8	323.2	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK400R3-525AXSP12	146	226.8	173.9	195	374.2	145.7	224.1	172.6	193.1	368	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK400R3-532AXSP16	139.7	215.4	165.2	185.2	-	138.6	212.4	163.6	183	-	180	34	2"	144	22.4	2"	216	47.7	2"
EAW-VD1552ZK400R3-625AXSP16	163.2	245.8	191.1	212.6	-	162	242.5	188.7	209.8	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK400R3-632AXSP16	155.2	236.1	182.7	204	-	154.2	232.9	180.5	201.1	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550B3-425AXSP12	145.8	228.9	174.4	196.3	-	145.7	226.6	173.2	194.5	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550B3-432AXSP12	134.7	213.3	162	182.7	-	134.6	211.3	160.9	181	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550B3-525AXSP12	160.6	249.3	191.2	214.5	412.8	160.4	246.9	189.7	212.4	406.2	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550B3-532AXSP12	150	235.5	179.7	202	393.3	149.8	233	178.4	200.1	386.9	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550B3-625AXSP12	174.2	268	206.6	231.1	437.8	173.9	265	205.1	228.6	430.9	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550B3-632AXSP16	170.3	259.9	200.6	224.2	-	169.1	256.6	198.3	221.5	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550C2-425AXSP12	152	239.2	182.2	205.2	-	151.9	237.1	181	203.3	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550C2-432AXSP12	140.2	222.2	168.4	190.1	-	140.1	220	167.2	188.5	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550C2-525AXSP12	168.4	261.9	200.5	225.2	-	168.1	259.2	198.8	222.8	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550C2-532AXSP12	156.7	246.3	187.6	211.4	411.8	156.4	243.6	186.5	209.3	405	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550C2-625AXSP12	183.7	282.7	217.9	243.8	463.4	183.3	279.7	216.2	241.1	455.2	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550C2-632AXSP12	173.1	269.8	206.9	232.1	445.7	172.9	266.5	205.3	229.5	438	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550C3-425AXSP12	152	239.2	182.2	205.2	-	151.9	237.1	181	203.3	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550C3-432AXSP12	140.2	222.2	168.4	190.1	-	140.1	220	167.2	188.5	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550C3-525AXSP12	168.4	261.9	200.5	225.2	-	168.1	259.2	198.8	222.8	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550C3-532AXSP12	156.7	246.3	187.6	211.4	411.8	156.4	243.6	186.5	209.3	405	248	24.1	3"</						

EAW-VD1552ZK550K3-632AXSP16	170.7	260.8	201	224.6	-	169.4	257	199	221.9	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550K4-425AXSP12	146.1	229.8	175	197	-	146	227.5	173.6	195.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K4-432AXSP12	135.2	213.8	162.4	183.1	-	135.2	211.9	161.2	181.7	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K4-525AXSP12	160.9	250.1	191.5	215	-	160.7	247.4	190.3	212.8	407.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K4-532AXSP12	150.3	236	180	202.7	394.1	150.3	233.9	178.8	200.8	387.8	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K4-625AXSP12	174.8	269	207.3	231.9	439.9	174.5	265.8	205.7	229.4	432.3	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550K4-632AXSP16	170.7	260.8	201	224.6	-	169.4	257	199	221.9	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550K5-425AXSP12	146.1	229.8	175	197	-	146	227.5	173.6	195.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K5-432AXSP12	135.2	213.8	162.4	183.1	-	135.2	211.9	161.2	181.7	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K5-525AXSP12	160.9	250.1	191.5	215	-	160.7	247.4	190.3	212.8	407.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K5-532AXSP12	150.3	236	180	202.7	394.1	150.3	233.9	178.8	200.8	387.8	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K5-625AXSP12	174.8	269	207.3	231.9	439.9	174.5	265.8	205.7	229.4	432.3	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550K5-632AXSP16	170.7	260.8	201	224.6	-	169.4	257	199	221.9	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550K8-425AXSP12	146.1	229.8	175	197	-	146	227.5	173.6	195.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K8-432AXSP12	135.2	213.8	162.4	183.1	-	135.2	211.9	161.2	181.7	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K8-525AXSP12	160.9	250.1	191.5	215	-	160.7	247.4	190.3	212.8	407.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K8-532AXSP12	150.3	236	180	202.7	394.1	150.3	233.9	178.8	200.8	387.8	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K8-625AXSP12	174.8	269	207.3	231.9	439.9	174.5	265.8	205.7	229.4	432.3	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550K8-632AXSP16	170.7	260.8	201	224.6	-	169.4	257	199	221.9	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550K9-425AXSP12	146.1	229.8	175	197	-	146	227.5	173.6	195.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K9-432AXSP12	135.2	213.8	162.4	183.1	-	135.2	211.9	161.2	181.7	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550K9-525AXSP12	160.9	250.1	191.5	215	-	160.7	247.4	190.3	212.8	407.5	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K9-532AXSP12	150.3	236	180	202.7	394.1	150.3	233.9	178.8	200.8	387.8	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550K9-625AXSP12	174.8	269	207.3	231.9	439.9	174.5	265.8	205.7	229.4	432.3	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550K9-632AXSP16	170.7	260.8	201	224.6	-	169.4	257	199	221.9	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD1552ZK550R3-425AXSP12	150.4	236.4	179.8	202.5	-	150.1	234.1	178.8	200.8	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550R3-432AXSP12	138.8	219.9	166.8	188.2	-	138.9	218	166	186.8	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK550R3-525AXSP12	165.6	257.4	197.2	221.4	-	165.4	254.6	195.7	219.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550R3-532AXSP12	154.6	242.8	185.3	208.4	405.8	154.5	240.7	184.1	206.5	399.4	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK550R3-625AXSP12	179.9	277.1	213.4	238.7	453.4	179.6	273.9	211.9	236.2	445.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK550R3-632AXSP12	170.2	265.1	203.4	228.1	437.8	170.3	262.2	201.7	225.8	430.7	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C2-425AXSP12	163.5	258.1	195.9	221	-	163.4	255.7	194.9	219.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C2-432AXSP12	150.6	239.2	181.1	204.7	-	150.7	236.9	180.1	203	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C2-525AXSP12	180.8	281.8	215.6	242.3	-	180.6	279.4	214.1	240.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C2-532AXSP12	168.5	265.1	202	227.4	-	168.5	262.9	200.7	225.5	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C2-625AXSP12	197.8	304.3	234.1	262.2	500.1	197.4	301.5	232.7	260	492.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C2-632AXSP12	186.5	290.7	222.4	249.7	481.7	186.3	287.6	221.1	247.3	474.1	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C3-425AXSP12	163.5	258.1	195.9	221	-	163.4	255.7	194.9	219.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C3-432AXSP12	150.6	239.2	181.1	204.7	-	150.7	236.9	180.1	203	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C3-525AXSP12	180.8	281.8	215.6	242.3	-	180.6	279.4	214.1	240.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C3-532AXSP12	168.5	265.1	202	227.4	-	168.5	262.9	200.7	225.5	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C3-625AXSP12	197.8	304.3	234.1	262.2	500.1	197.4	301.5	232.7	260	492.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C3-632AXSP12	186.5	290.7	222.4	249.7	481.7	186.3	287.6	221.1	247.3	474.1	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C4-425AXSP12	163.5	258.1	195.9	221	-	163.4	255.7	194.9	219.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C4-432AXSP12	150.6	239.2	181.1	204.7	-	150.7	236.9	180.1	203	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C4-525AXSP12	180.8	281.8	215.6	242.3	-	180.6	279.4	214.1	240.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C4-532AXSP12	168.5	265.1	202	227.4	-	168.5	262.9	200.7	225.5	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C4-625AXSP12	197.8	304.3	234.1	262.2	500.1	197.4	301.5	232.7	260	492.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C4-632AXSP12	186.5	290.7	222.4	249.7	481.7	186.3	287.6	221.1	247.3	474.1	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C5-425AXSP12	163.5	258.1	195.9	221	-	163.4	255.7	194.9	219.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C5-432AXSP12	150.6	239.2	181.1	204.7	-	150.7	236.9	180.1	203	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C5-525AXSP12	180.8	281.8	215.6	242.3	-	180.6	279.4	214.1	240.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C5-532AXSP12	168.5	265.1	202	227.4	-	168.5	262.9	200.7	225.5	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C5-625AXSP12	197.8	304.3	234.1	262.2	500.1	197.4	301.5	232.7	260	492.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C5-632AXSP12	186.5	290.7	222.4	249.7	481.7	186.3	287.6	221.1	247.3	474.1	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C8-425AXSP12	163.5	258.1	195.9	221	-	163.4	255.7	194.9	219.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C8-432AXSP12	150.6	239.2	181.1	204.7	-	150.7	236.9	180.1	203	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C8-525AXSP12	180.8	281.8	215.6	242.3	-	180.6	279.4	214.1	240.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C8-532AXSP12	168.5	265.1	202	227.4	-	168.5	262.9	200.7	225.5	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750C8-625AXSP12	197.8	304.3	234.1	262.2	500.1	197.4	301.5	232.7	260	492.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C8-632AXSP12	186.5	290.7	222.4	249.7	481.7	186.3	287.6	221.1	247.3	474.1	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750C9-425AXSP12	163.5	258.1	195.9	221	-	163.4	255.7	194.9	219.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C9-432AXSP12	150.6	239.2	181.1	204.7	-	150.7	236.9	180.1	203	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750C9-525AXSP12	180.8	281.8	215.6	242.3	-	180.6	279.4	214.1	240.2	-	248	24.1	3"	198	19.3	2"	29		

EAW-VD1552ZK750K9-625AXSP12	190.3	293.2	225.5	252.4	480.8	190.1	290	224	250.3	472.9	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750K9-632AXSP12	180	280.1	214.5	240.8	463.8	179.8	277.2	213.3	238.8	456.6	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750R3-425AXSP08	155.1	243.9	185.6	209.1	-	154.9	241.7	184.6	207.5	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750R3-432AXSP12	143.2	227.2	172.1	194.3	-	143.3	225.4	171.4	193	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD1552ZK750R3-525AXSP12	170.9	266	203.3	228.3	-	170.6	263.4	202.2	226.3	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750R3-532AXSP12	159.7	250.7	191.1	215.1	-	159.6	248.4	190	213.3	413.2	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD1552ZK750R3-625AXSP12	185.8	286.1	220.5	246.4	469	185.6	283	218.7	244.3	461.2	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1552ZK750R3-632AXSP12	175.7	273.7	210	235.3	452.8	175.8	271.1	208.5	233.4	445.8	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD1553PB370C2-425AXSP08	165.9	263.3	199.7	225.5	-	166.3	261.8	199	224.4	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C2-432AXSP08	153.3	245.5	185.1	209.7	-	153.8	243.8	184.7	208.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C2-525AXSP08	184.1	289	220.6	248	-	185	287.4	219.7	246.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C2-532AXSP08	172.3	273.9	207.8	234.5	460.9	173.2	272.1	207.5	233.2	455.1	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C2-625AXSP08	196.3	306.2	234.6	263.2	504.8	197.3	304	234	262	498.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C2-632AXSP08	186.7	294.6	224.6	252.8	490.2	187.5	292.4	224	251.1	483.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C4-425AXSP08	165.9	263.3	199.7	225.5	-	166.3	261.8	199	224.4	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C4-432AXSP08	153.3	245.5	185.1	209.7	-	153.8	243.8	184.7	208.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C4-525AXSP08	184.1	289	220.6	248	-	185	287.4	219.7	246.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C4-532AXSP08	172.3	273.9	207.8	234.5	460.9	173.2	272.1	207.5	233.2	455.1	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C4-625AXSP08	196.3	306.2	234.6	263.2	504.8	197.3	304	234	262	498.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C4-632AXSP08	186.7	294.6	224.6	252.8	490.2	187.5	292.4	224	251.1	483.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C5-425AXSP08	165.9	263.3	199.7	225.5	-	166.3	261.8	199	224.4	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C5-432AXSP08	153.3	245.5	185.1	209.7	-	153.8	243.8	184.7	208.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C5-525AXSP08	184.1	289	220.6	248	-	185	287.4	219.7	246.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C5-532AXSP08	172.3	273.9	207.8	234.5	460.9	173.2	272.1	207.5	233.2	455.1	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C5-625AXSP08	196.3	306.2	234.6	263.2	504.8	197.3	304	234	262	498.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C5-632AXSP08	186.7	294.6	224.6	252.8	490.2	187.5	292.4	224	251.1	483.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C8-425AXSP08	165.9	263.3	199.7	225.5	-	166.3	261.8	199	224.4	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C8-432AXSP08	153.3	245.5	185.1	209.7	-	153.8	243.8	184.7	208.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370C8-525AXSP08	184.1	289	220.6	248	-	185	287.4	219.7	246.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C8-532AXSP08	172.3	273.9	207.8	234.5	460.9	173.2	272.1	207.5	233.2	455.1	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370C8-625AXSP08	196.3	306.2	234.6	263.2	504.8	197.3	304	234	262	498.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370C8-632AXSP08	186.7	294.6	224.6	252.8	490.2	187.5	292.4	224	251.1	483.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K8-425AXSP08	159.8	253.5	192.3	217	-	160.1	251.9	191.8	215.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K8-432AXSP08	147.9	236.5	178.7	202.2	-	148.5	235.2	178.2	201	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K8-525AXSP08	177.1	277.9	212.1	238.3	463.3	177.6	276.2	211.5	237.2	457.3	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K8-532AXSP08	166.1	263.8	200.1	225.7	443.2	166.8	261.9	199.7	224.7	437.5	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K8-625AXSP08	188.9	294.2	226	253.1	484.7	189.6	292.2	225.1	251.6	478.5	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K8-632AXSP08	179.4	283	216.1	243	471	180.4	281.2	215.4	241.7	464.2	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K4-425AXSP08	159.8	253.5	192.3	217	-	160.1	251.9	191.8	215.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K4-432AXSP08	147.9	236.5	178.7	202.2	-	148.5	235.2	178.2	201	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K4-525AXSP08	177.1	277.9	212.1	238.3	463.3	177.6	276.2	211.5	237.2	457.3	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K4-532AXSP08	166.1	263.8	200.1	225.7	443.2	166.8	261.9	199.7	224.7	437.5	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K4-625AXSP08	188.9	294.2	226	253.1	484.7	189.6	292.2	225.1	251.6	478.5	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K4-632AXSP08	179.4	283	216.1	243	471	180.4	281.2	215.4	241.7	464.2	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K5-425AXSP08	159.8	253.5	192.3	217	-	160.1	251.9	191.8	215.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K5-432AXSP08	147.9	236.5	178.7	202.2	-	148.5	235.2	178.2	201	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K5-525AXSP08	177.1	277.9	212.1	238.3	463.3	177.6	276.2	211.5	237.2	457.3	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K5-532AXSP08	166.1	263.8	200.1	225.7	443.2	166.8	261.9	199.7	224.7	437.5	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K5-625AXSP08	188.9	294.2	226	253.1	484.7	189.6	292.2	225.1	251.6	478.5	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K5-632AXSP08	179.4	283	216.1	243	471	180.4	281.2	215.4	241.7	464.2	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K8-425AXSP08	159.8	253.5	192.3	217	-	160.1	251.9	191.8	215.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K8-432AXSP08	147.9	236.5	178.7	202.2	-	148.5	235.2	178.2	201	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB370K8-525AXSP08	177.1	277.9	212.1	238.3	463.3	177.6	276.2	211.5	237.2	457.3	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K8-532AXSP08	166.1	263.8	200.1	225.7	443.2	166.8	261.9	199.7	224.7	437.5	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB370K8-625AXSP08	188.9	294.2	226	253.1	484.7	189.6	292.2	225.1	251.6	478.5	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB370K8-632AXSP08	179.4	283	216.1	243	471	180.4	281.2	215.4	241.7	464.2	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB400B3-425AXSP08	161	256.1	193.8	219.1	-	161.8	254.6	193.4	218.1	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB400B3-432AXSP08	149.5	239	180.5	204.2	-	150.2	237.8	180.1	203.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB400B3-525AXSP08	178	279.5	213.2	240	466.7	179	278.1	212.9	238.8	460.6	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB400B3-532AXSP08	167.6	265.9	201.9	227.8	446.9	168.4	264.5	201.7	226.6	442	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB400B3-625AXSP08	189.1	295	226.3	253.7	486	190.3	293.2	225.9	252.4	480.2	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB400B3-632AXSP08	180.6	284.6	217.2	244.3	473.7	181.2	283.1	216.8	243.3	468	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB400C3-425AXSP08	165.9	263.3	199.7	225.5	-	166.3	261.8	199	224.4	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB400C3-432AXSP08	153.3	245.5	185.1	209.7	-	153.8	243.8	184.7	208.5	-	225	24.8	2"	180	16.3	2"	270	29.	

EAW-VD1553PB550C2-532AXSP08	192.7	306.3	232	261.9	-	193.7	304.7	231.7	260.8	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C2-625AXSP08	221.7	345.5	264.2	296.8	-	222.5	343.4	263.7	295.6	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C2-632AXSP08	209.8	330.5	251.7	283.3	553.4	210.8	329	251.5	282.3	546.3	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C3-425AXSP08	184.7	294.5	222.5	251.8	-	185.6	293.1	222.4	250.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C3-432AXSP08	170	273.1	205.9	233.2	-	170.9	272	205.6	232.3	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C3-525AXSP08	206.2	325.3	247.2	278.4	-	206.9	323.4	246.6	277.5	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C3-532AXSP08	192.7	306.3	232	261.9	-	193.7	304.7	231.7	260.8	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C3-625AXSP08	221.7	345.5	264.2	296.8	-	222.5	343.4	263.7	295.6	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C3-632AXSP08	209.8	330.5	251.7	283.3	553.4	210.8	329	251.5	282.3	546.3	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C4-425AXSP08	184.7	294.5	222.5	251.8	-	185.6	293.1	222.4	250.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C4-432AXSP08	170	273.1	205.9	233.2	-	170.9	272	205.6	232.3	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C4-525AXSP08	206.2	325.3	247.2	278.4	-	206.9	323.4	246.6	277.5	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C4-532AXSP08	192.7	306.3	232	261.9	-	193.7	304.7	231.7	260.8	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C4-625AXSP08	221.7	345.5	264.2	296.8	-	222.5	343.4	263.7	295.6	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C4-632AXSP08	209.8	330.5	251.7	283.3	553.4	210.8	329	251.5	282.3	546.3	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C5-425AXSP08	184.7	294.5	222.5	251.8	-	185.6	293.1	222.4	250.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C5-432AXSP08	170	273.1	205.9	233.2	-	170.9	272	205.6	232.3	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C5-525AXSP08	206.2	325.3	247.2	278.4	-	206.9	323.4	246.6	277.5	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C5-532AXSP08	192.7	306.3	232	261.9	-	193.7	304.7	231.7	260.8	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C5-625AXSP08	221.7	345.5	264.2	296.8	-	222.5	343.4	263.7	295.6	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C5-632AXSP08	209.8	330.5	251.7	283.3	553.4	210.8	329	251.5	282.3	546.3	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C8-425AXSP08	184.7	294.5	222.5	251.8	-	185.6	293.1	222.4	250.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C8-432AXSP08	170	273.1	205.9	233.2	-	170.9	272	205.6	232.3	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C8-525AXSP08	206.2	325.3	247.2	278.4	-	206.9	323.4	246.6	277.5	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C8-532AXSP08	192.7	306.3	232	261.9	-	193.7	304.7	231.7	260.8	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C8-625AXSP08	221.7	345.5	264.2	296.8	-	222.5	343.4	263.7	295.6	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C8-632AXSP08	209.8	330.5	251.7	283.3	553.4	210.8	329	251.5	282.3	546.3	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C9-425AXSP08	184.7	294.5	222.5	251.8	-	185.6	293.1	222.4	250.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C9-432AXSP08	170	273.1	205.9	233.2	-	170.9	272	205.6	232.3	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550C9-525AXSP08	206.2	325.3	247.2	278.4	-	206.9	323.4	246.6	277.5	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C9-532AXSP08	192.7	306.3	232	261.9	-	193.7	304.7	231.7	260.8	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550C9-625AXSP08	221.7	345.5	264.2	296.8	-	222.5	343.4	263.7	295.6	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550C9-632AXSP08	209.8	330.5	251.7	283.3	553.4	210.8	329	251.5	282.3	546.3	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K2-425AXSP08	176.6	281.1	212.9	240.7	-	177.4	279.8	212.4	239.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K2-432AXSP08	163.2	262	197.4	223.7	-	163.9	260.5	197.2	222.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K2-525AXSP08	196.4	309	235.2	265.2	-	197.3	307.6	234.6	263.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K2-532AXSP08	184.1	292.2	221.8	250.1	-	184.9	290.6	221.4	249.1	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K2-625AXSP08	210.6	327.9	251.1	281.9	542.8	211.4	326.1	250.5	280.3	535.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K2-632AXSP08	199.4	314.6	239.7	269.6	525.2	200.5	312.6	239.3	268.5	519	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K3-425AXSP08	176.6	281.1	212.9	240.7	-	177.4	279.8	212.4	239.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K3-432AXSP08	163.2	262	197.4	223.7	-	163.9	260.5	197.2	222.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K3-525AXSP08	196.4	309	235.2	265.2	-	197.3	307.6	234.6	263.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K3-532AXSP08	184.1	292.2	221.8	250.1	-	184.9	290.6	221.4	249.1	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K3-625AXSP08	210.6	327.9	251.1	281.9	542.8	211.4	326.1	250.5	280.3	535.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K3-632AXSP08	199.4	314.6	239.7	269.6	525.2	200.5	312.6	239.3	268.5	519	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K4-425AXSP08	176.6	281.1	212.9	240.7	-	177.4	279.8	212.4	239.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K4-432AXSP08	163.2	262	197.4	223.7	-	163.9	260.5	197.2	222.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K4-525AXSP08	196.4	309	235.2	265.2	-	197.3	307.6	234.6	263.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K4-532AXSP08	184.1	292.2	221.8	250.1	-	184.9	290.6	221.4	249.1	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K4-625AXSP08	210.6	327.9	251.1	281.9	542.8	211.4	326.1	250.5	280.3	535.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K4-632AXSP08	199.4	314.6	239.7	269.6	525.2	200.5	312.6	239.3	268.5	519	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K5-425AXSP08	176.6	281.1	212.9	240.7	-	177.4	279.8	212.4	239.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K5-432AXSP08	163.2	262	197.4	223.7	-	163.9	260.5	197.2	222.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K5-525AXSP08	196.4	309	235.2	265.2	-	197.3	307.6	234.6	263.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K5-532AXSP08	184.1	292.2	221.8	250.1	-	184.9	290.6	221.4	249.1	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K5-625AXSP08	210.6	327.9	251.1	281.9	542.8	211.4	326.1	250.5	280.3	535.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K5-632AXSP08	199.4	314.6	239.7	269.6	525.2	200.5	312.6	239.3	268.5	519	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K8-425AXSP08	176.6	281.1	212.9	240.7	-	177.4	279.8	212.4	239.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K8-432AXSP08	163.2	262	197.4	223.7	-	163.9	260.5	197.2	222.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K8-525AXSP08	196.4	309	235.2	265.2	-	197.3	307.6	234.6	263.9	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K8-532AXSP08	184.1	292.2	221.8	250.1	-	184.9	290.6	221.4	249.1	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB550K8-625AXSP08	210.6	327.9	251.1	281.9	542.8	211.4	326.1	250.5	280.3	535.9	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K8-632AXSP08	199.4	314.6	239.7	269.6	525.2	200.5	312.6	239.3	268.5	519	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB550K9-425AXSP08	176.6	281.1	212.9	240.7	-	177.4	279.8	212.4	239.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K9-432AXSP08	163.2	262	197.4	223.7	-	163.9	260.5	197.2	222.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB550K9-525AXSP08	196.4	309	235.2	265.2	-	197.3	307.6	234.6</											

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1553PB750C8-525AXSP08	217.6	343.3	261.1	294.3	-	218.5	342	261.1	293.6	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750C8-532AXSP08	203.5	324.2	245.3	277.2	-	204.6	323	245	276.6	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750C8-625AXSP08	233.3	364.3	278.1	312.6	-	234.6	362.9	278.3	311.7	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750C8-632AXSP08	221.5	348.8	265.5	299	-	222.6	347.3	265.3	298.1	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750C9-425AXSP08	195.1	312.2	235.7	266.5	-	196.3	310.8	235.6	265.7	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750C9-432AXSP08	180	289.9	218.1	247.3	-	181	288.8	218.1	246.5	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750C9-525AXSP08	217.6	343.3	261.1	294.3	-	218.5	342	261.1	293.6	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750C9-532AXSP08	203.5	324.2	245.3	277.2	-	204.6	323	245	276.6	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750C9-625AXSP08	233.3	364.3	278.1	312.6	-	234.6	362.9	278.3	311.7	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750C9-632AXSP08	221.5	348.8	265.5	299	-	222.6	347.3	265.3	298.1	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K2-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K2-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K2-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K2-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K2-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K2-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K3-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K3-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K3-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K3-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K3-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K3-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K4-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K4-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K4-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K4-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K4-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K4-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K5-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K5-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K5-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K5-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K5-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K5-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K8-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K8-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K8-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K8-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K8-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K8-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K9-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K9-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750K9-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K9-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750K9-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750K9-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750R3-425AXSP08	188.9	301.7	227.8	257.8	-	189.8	300.3	227.6	257	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750R3-432AXSP08	174.7	280.5	211.4	239.6	-	175.6	279.5	211.4	238.8	-	225	24.8	2"	180	16.3	2"	270	29.2	3"
EAW-VD1553PB750R3-525AXSP08	210.2	331.4	252	284	-	211.2	330.4	251.8	283	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750R3-532AXSP08	197.1	313.3	237.4	268.1	-	198.1	312.1	237	267	-	282	21.4	3"	225	18.1	2"	338	30	3"
EAW-VD1553PB750R3-625AXSP08	225.5	351.7	268.8	302	-	226.7	350.2	268.9	301	-	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750R3-632AXSP08	213.8	337	256.5	289.2	-	215	335.4	256.5	288.1	558	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750R3-632AXSP08	209	329.6	251.1	282.6	551.1	210.1	327.9	250.6	281.4	545.2	338	22	3"	270	14.5	3"	406	30.9	3"
EAW-VD1553PB750R3-632AXSP08	196.9	306.6	234.5	263.4	-	196	303.4	232.5	260.6	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD1553PB750R3-632AXSP08	182.2	285.7	217.7	245	-	181.3	282.6	215.7	242.5	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD1553PB750R3-632AXSP08	219.5	337.3	259.5	290.6	-	218.4	333.5	257	287.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1553PB750R3-632AXSP08	205.8	319	244.7	274.4	-	205	315.5	242.4	271.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1553PB750R3-632AXSP08	236.2	358.6	277.4	309.7	-	234.8	354	274.6	306	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1553PB750R3-632AXSP08	224.3	343.7	264.6	296.1	563.9	223	339.3	262.3	292.9	554.7	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1553PB750R3-632AXSP08	196.9	306.6	234.5	263.4	-	196	303.4	232.5	260.6	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD1553PB750R3-632AXSP08	182.2	285.7	217.7	245	-	181.3	282.6	215.7	242.5	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD1553PB750R3-632AXSP08	219.5	337.3	259.5	290.6	-	218.4	333.5	257	287.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1553PB750R3-632AXSP08	205.8	319	244.7	274.4	-	205	315.5	242.4	271.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1553PB750R3-632AXSP08	236.2	358.6	277.4	309.7	-	234.8	354	274.6	306	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1553PB750R3-632AXSP08	224.3	343.7	264.6	296.1	563.9	223	339.3	262.3	292.9	554.7	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1553PB750R3-632AXSP08	196.9	306.6	234.5	263.4	-	196	303.4	232.5	260.6	-	225	30.7	2"	180	20.3	2"	270	3	

EAW-VD15S3PI400B3-432AXSP08	178.2	279.1	212.8	239.4	-	177.7	276.1	211	237.1	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400B3-525AXSP08	213.6	328.2	252.4	282.6	-	212.9	324.2	250.4	279.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400B3-532AXSP08	200.7	311.2	238.6	267.4	-	200	307.5	236.4	264.5	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400B3-625AXSP08	229.2	347.1	269.1	299.9	564.5	227.9	342.9	266.5	296.5	554.5	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400B3-632AXSP08	217.9	334.2	257.8	288	547.9	217.1	330	255.2	285	538.5	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400C3-425AXSP08	196.9	306.6	234.5	263.4	-	196	303.4	232.5	260.6	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400C3-432AXSP08	182.2	285.7	217.7	245	-	181.3	282.6	215.7	242.5	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400C3-525AXSP08	219.5	337.3	259.5	290.6	-	218.4	333.5	257	287.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400C3-532AXSP08	205.8	319	244.7	274.4	-	205	315.5	242.4	271.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400C3-625AXSP08	236.2	358.6	277.4	309.7	-	234.8	354	274.6	306	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400C3-632AXSP08	224.3	343.7	264.6	296.1	563.9	223	339.3	262.3	292.9	554.7	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400C9-425AXSP08	196.9	306.6	234.5	263.4	-	196	303.4	232.5	260.6	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400C9-432AXSP08	182.2	285.7	217.7	245	-	181.3	282.6	215.7	242.5	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400C9-525AXSP08	219.5	337.3	259.5	290.6	-	218.4	333.5	257	287.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400C9-532AXSP08	205.8	319	244.7	274.4	-	205	315.5	242.4	271.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400C9-625AXSP08	236.2	358.6	277.4	309.7	-	234.8	354	274.6	306	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400C9-632AXSP08	224.3	343.7	264.6	296.1	563.9	223	339.3	262.3	292.9	554.7	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400K3-425AXSP08	189.7	295.1	225.7	253.4	-	189.1	291.7	223.8	250.7	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400K3-432AXSP08	175.8	275.6	210	236.1	-	175.3	272.6	208.4	233.8	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400K3-525AXSP08	210.8	323.8	249.1	278.8	-	210	319.7	247	275.6	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400K3-532AXSP08	198.1	306.9	235.4	263.8	-	197.3	303.1	233.2	260.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400K3-625AXSP08	226.5	343.4	265.9	296.4	557.6	225.3	339	263.1	292.8	547.4	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400K3-632AXSP08	215.1	329.7	254	284.2	540.5	214.2	325.8	251.8	281.1	531	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400K9-425AXSP08	189.7	295.1	225.7	253.4	-	189.1	291.7	223.8	250.7	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400K9-432AXSP08	175.8	275.6	210	236.1	-	175.3	272.6	208.4	233.8	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400K9-525AXSP08	210.8	323.8	249.1	278.8	-	210	319.7	247	275.6	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400K9-532AXSP08	198.1	306.9	235.4	263.8	-	197.3	303.1	233.2	260.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400K9-625AXSP08	226.5	343.4	265.9	296.4	557.6	225.3	339	263.1	292.8	547.4	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400K9-632AXSP08	215.1	329.7	254	284.2	540.5	214.2	325.8	251.8	281.1	531	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400R3-425AXSP08	193.4	301.2	230.2	258.5	-	192.9	297.8	228.4	255.9	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400R3-432AXSP08	179.3	281.4	214.2	241.4	-	178.8	278.5	212.7	238.7	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI400R3-525AXSP08	215.2	330.3	254.3	284.7	-	214.1	326.3	251.9	281.5	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400R3-532AXSP08	202.3	313.2	240	269.1	-	201.2	309.5	237.9	266.6	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI400R3-625AXSP08	231	350.4	271.2	302.3	-	229.6	346	268.5	298.8	559.6	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI400R3-632AXSP08	219.5	336.7	259.3	290.1	552.1	218.4	332.5	256.8	286.7	542.6	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550B3-425AXSP06	200	317.7	240.6	271.4	-	200.3	315.1	239.5	270	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550B3-432AXSP08	195.3	306.6	233.2	262.8	-	194.7	303.6	231.5	260.6	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI550B3-525AXSP08	235.3	362.5	278.3	311.9	-	234.2	358.4	276.1	308.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550B3-532AXSP08	220.5	342.9	262.4	294.5	-	219.7	339.2	260.4	291.7	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550B3-625AXSP08	252.7	384.4	297.3	331.7	-	251.7	380.2	294.8	328.3	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550B3-632AXSP08	239.9	369.2	284	317.7	-	239	365	281.6	314.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C2-425AXSP06	208.8	332.1	251.4	284.4	-	209.1	329.8	250.6	282.3	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C2-432AXSP06	192.1	307.6	232.2	262.7	-	192.5	305.3	231.4	261.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C2-525AXSP08	247	381.9	292.8	328.3	-	246.1	377.4	290.2	324.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C2-532AXSP08	230.8	359.2	274.8	308.7	-	229.8	355.1	272.1	305.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C2-625AXSP08	267	407.4	314.7	351.2	-	265.6	402.5	311.7	347.2	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C2-632AXSP08	252.1	388.8	298.7	334.7	-	251.1	384.2	296	331	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C3-425AXSP06	208.8	332.1	251.4	284.4	-	209.1	329.8	250.6	282.3	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C3-432AXSP06	192.1	307.6	232.2	262.7	-	192.5	305.3	231.4	261.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C3-525AXSP08	247	381.9	292.8	328.3	-	246.1	377.4	290.2	324.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C3-532AXSP08	230.8	359.2	274.8	308.7	-	229.8	355.1	272.1	305.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C3-625AXSP08	267	407.4	314.7	351.2	-	265.6	402.5	311.7	347.2	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C3-632AXSP08	252.1	388.8	298.7	334.7	-	251.1	384.2	296	331	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C4-425AXSP06	208.8	332.1	251.4	284.4	-	209.1	329.8	250.6	282.3	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C4-432AXSP06	192.1	307.6	232.2	262.7	-	192.5	305.3	231.4	261.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C4-525AXSP08	247	381.9	292.8	328.3	-	246.1	377.4	290.2	324.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C4-532AXSP08	230.8	359.2	274.8	308.7	-	229.8	355.1	272.1	305.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C4-625AXSP08	267	407.4	314.7	351.2	-	265.6	402.5	311.7	347.2	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C4-632AXSP08	252.1	388.8	298.7	334.7	-	251.1	384.2	296	331	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C5-425AXSP06	208.8	332.1	251.4	284.4	-	209.1	329.8	250.6	282.3	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C5-432AXSP06	192.1	307.6	232.2	262.7	-	192.5	305.3	231.4	261.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550C5-525AXSP08	247	381.9	292.8	328.3	-	246.1	377.4	290.2	324.8	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C5-532AXSP08	230.8	359.2	274.8	308.7	-	229.8	355.1	272.1	305.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550C5-625AXSP08	267	407.4	314.7	351.2	-	265.6	402.5	311.7	347.2	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550C5-632AXSP08	252.1	388.8	298.7	334.7	-	251.1	384.2	296	331	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3																			

EAW-VD15S3PI550K8-425AXSP06	200.2	318.2	241.3	272.3	-	201	316.1	240.3	270.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550K8-432AXSP08	195.6	307.7	234.1	263.7	-	195	304.7	232.3	261.1	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI550K8-525AXSP08	236.1	363.8	279.3	313	-	235.2	359.6	276.9	309.7	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550K8-532AXSP08	221.3	343.6	262.9	295.1	-	220.4	339.8	260.8	292.1	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550K8-625AXSP08	253.9	386.8	299.1	333.7	-	253	382.3	296.4	330.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550K8-632AXSP08	241.1	370.5	285	319.2	-	240.1	366.2	282.5	315.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550K9-425AXSP06	200.2	318.2	241.3	272.3	-	201	316.1	240.3	270.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550K9-432AXSP08	195.6	307.7	234.1	263.7	-	195	304.7	232.3	261.1	-	225	30.7	2"	180	20.3	2"	270	37.5	3"
EAW-VD15S3PI550K9-525AXSP08	236.1	363.8	279.3	313	-	235.2	359.6	276.9	309.7	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550K9-532AXSP08	221.3	343.6	262.9	295.1	-	220.4	339.8	260.8	292.1	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550K9-625AXSP08	253.9	386.8	299.1	333.7	-	253	382.3	296.4	330.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550K9-632AXSP08	241.1	370.5	285	319.2	-	240.1	366.2	282.5	315.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550R3-425AXSP06	205.7	326.9	247.6	279.5	-	206.2	324.8	246.6	278.2	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550R3-432AXSP06	189.5	303.6	229.2	259.3	-	190.3	301.6	228.7	258	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI550R3-525AXSP08	242.4	373.9	287.2	322	-	241.6	370.2	284.9	318.7	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550R3-532AXSP08	227	353.1	270.3	303.5	-	226.2	349.8	267.9	300.6	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI550R3-625AXSP08	260.8	397.7	307.3	343	-	259.8	393.4	304.8	339.5	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI550R3-632AXSP08	247.4	380.7	293	327.8	-	246.5	376.9	290.5	324.4	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C2-425AXSP06	223.5	355.9	269.5	304.2	-	223.9	353.5	268.8	302.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C2-432AXSP06	205.4	329.8	248.7	281.6	-	206.2	327.8	247.9	279.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C2-525AXSP06	252.9	397.8	302.9	341.4	-	253.6	395.1	301.9	339	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750C2-532AXSP08	246.9	385.1	294.3	330.9	-	246.3	381.3	291.9	327.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750C2-625AXSP08	284.9	436.3	336.4	375.7	-	284	431.8	333.8	372.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C2-632AXSP08	269.6	416.5	319.7	358.5	-	268.6	412.2	317.3	354.6	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C3-425AXSP06	223.5	355.9	269.5	304.2	-	223.9	353.5	268.8	302.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C3-432AXSP06	205.4	329.8	248.7	281.6	-	206.2	327.8	247.9	279.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C3-525AXSP06	252.9	397.8	302.9	341.4	-	253.6	395.1	301.9	339	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750C3-532AXSP08	246.9	385.1	294.3	330.9	-	246.3	381.3	291.9	327.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750C3-625AXSP08	284.9	436.3	336.4	375.7	-	284	431.8	333.8	372.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C3-632AXSP08	269.6	416.5	319.7	358.5	-	268.6	412.2	317.3	354.6	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C4-425AXSP06	223.5	355.9	269.5	304.2	-	223.9	353.5	268.8	302.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C4-432AXSP06	205.4	329.8	248.7	281.6	-	206.2	327.8	247.9	279.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C4-525AXSP06	252.9	397.8	302.9	341.4	-	253.6	395.1	301.9	339	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750C4-532AXSP08	246.9	385.1	294.3	330.9	-	246.3	381.3	291.9	327.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750C4-625AXSP08	284.9	436.3	336.4	375.7	-	284	431.8	333.8	372.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C4-632AXSP08	269.6	416.5	319.7	358.5	-	268.6	412.2	317.3	354.6	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C5-425AXSP06	223.5	355.9	269.5	304.2	-	223.9	353.5	268.8	302.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C5-432AXSP06	205.4	329.8	248.7	281.6	-	206.2	327.8	247.9	279.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C5-525AXSP06	252.9	397.8	302.9	341.4	-	253.6	395.1	301.9	339	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750C5-532AXSP08	246.9	385.1	294.3	330.9	-	246.3	381.3	291.9	327.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750C5-625AXSP08	284.9	436.3	336.4	375.7	-	284	431.8	333.8	372.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C5-632AXSP08	269.6	416.5	319.7	358.5	-	268.6	412.2	317.3	354.6	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C8-425AXSP06	223.5	355.9	269.5	304.2	-	223.9	353.5	268.8	302.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C8-432AXSP06	205.4	329.8	248.7	281.6	-	206.2	327.8	247.9	279.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C8-525AXSP06	252.9	397.8	302.9	341.4	-	253.6	395.1	301.9	339	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750C8-532AXSP08	246.9	385.1	294.3	330.9	-	246.3	381.3	291.9	327.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750C8-625AXSP08	284.9	436.3	336.4	375.7	-	284	431.8	333.8	372.1	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C8-632AXSP08	269.6	416.5	319.7	358.5	-	268.6	412.2	317.3	354.6	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750C9-425AXSP06	223.5	355.9	269.5	304.2	-	223.9	353.5	268.8	302.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C9-432AXSP06	205.4	329.8	248.7	281.6	-	206.2	327.8	247.9	279.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750C9-525AXSP06	252.9	397.8	302.9	341.4	-	253.6	395.1	301.9	339	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750C9-532AXSP08	246.9	385.1	294.3	330.9	-	246.3	381.3	291.9	327.4	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750K2-425AXSP06	216.3	344.3	260.7	294.6	-	216.7	341.9	259.9	292.9	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750K2-432AXSP06	199.2	319.4	241	272.9	-	200	317.5	240.2	271.2	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750K2-525AXSP06	244.2	383.9	292.7	329.3	-	245	381.2	291.2	327.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750K2-532AXSP08	238.6	372.1	284.3	319.5	-	238	368.5	282.5	316.7	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750K2-625AXSP08	274.6	419.4	323.7	361.8	-	273.7	415.2	321.3	358.5	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750K2-632AXSP08	260.2	401.9	308.4	345.7	-	259.5	397.6	306	342.3	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750K3-425AXSP06	216.3	344.3	260.7	294.6	-	216.7	341.9	259.9	292.9	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750K3-432AXSP06	199.2	319.4	241	272.9	-	200	317.5	240.2	271.2	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750K3-525AXSP06	244.2	383.9	292.7	329.3	-	245	381.2	291.2	327.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD15S3PI750K3-532AXSP08	238.6	372.1	284.3	319.5	-	238	368.5	282.5	316.7	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD15S3PI750K3-625AXSP08	274.6	419.4	323.7	361.8	-	273.7	415.2	321.3	358.5	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750K3-632AXSP08	260.2	401.9	308.4	345.7	-	259.5	397.6	306	342.3	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD15S3PI750K4-425AXSP06	216.3	344.3	260.7	294.6	-	216.7	341.9	259.9	292.9	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD15S3PI750K4-432AXSP06	199.2	319.4																	

EAW-VD1553PK370C2-632AXSP08	200.8	312.8	239.8	269.2	518.8	201	310.5	238.4	267.1	510.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370C4-425AXSP08	177.3	279.5	212.7	239.4	-	177.3	277.3	211.5	237.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370C4-432AXSP08	164	260.2	197.4	222.7	-	164.2	258.5	196.2	221.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370C4-526AXSP08	197.6	307.6	235	264	-	197.5	305	233.8	262	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370C4-532AXSP08	185.3	291.1	221.5	249.3	-	185.1	288.6	220.4	247.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370C4-625AXSP08	211.6	325.8	250.9	280.8	535.2	211.6	322.9	249.3	278.5	527.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370C4-632AXSP08	200.8	312.8	239.8	269.2	518.8	201	310.5	238.4	267.1	510.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370C5-425AXSP08	177.3	279.5	212.7	239.4	-	177.3	277.3	211.5	237.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370C5-432AXSP08	164	260.2	197.4	222.7	-	164.2	258.5	196.2	221.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370C5-525AXSP08	197.6	307.6	235	264	-	197.5	305	233.8	262	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370C5-532AXSP08	185.3	291.1	221.5	249.3	-	185.1	288.6	220.4	247.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370C5-625AXSP08	211.6	325.8	250.9	280.8	535.2	211.6	322.9	249.3	278.5	527.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370C5-632AXSP08	200.8	312.8	239.8	269.2	518.8	201	310.5	238.4	267.1	510.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370C8-425AXSP08	177.3	279.5	212.7	239.4	-	177.3	277.3	211.5	237.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370C8-432AXSP08	164	260.2	197.4	222.7	-	164.2	258.5	196.2	221.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370C8-525AXSP08	197.6	307.6	235	264	-	197.5	305	233.8	262	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370C8-532AXSP08	185.3	291.1	221.5	249.3	-	185.1	288.6	220.4	247.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370C8-625AXSP08	211.6	325.8	250.9	280.8	535.2	211.6	322.9	249.3	278.5	527.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370C8-632AXSP08	200.8	312.8	239.8	269.2	518.8	201	310.5	238.4	267.1	510.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K2-432AXSP08	170.7	269	204.7	230.6	-	171	266.8	203.5	228.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K2-432AXSP08	158.1	251	190.1	214.7	-	158.4	248.8	189.2	213.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K2-525AXSP08	189.9	295.1	226.1	253.5	-	189.8	292.5	224.8	251.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K2-532AXSP08	178.1	279.6	213.1	240.1	467.4	178.2	277.2	212	238.2	460.7	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K2-625AXSP08	202.9	312.4	240.8	269.4	512.1	202.8	309.5	239.2	267.2	504.4	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K2-632AXSP08	192.8	300.7	230.4	258.5	497.4	192.9	297.9	229	256.4	489.7	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K4-425AXSP08	170.7	269	204.7	230.6	-	171	266.8	203.5	228.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K4-432AXSP08	158.1	251	190.1	214.7	-	158.4	248.8	189.2	213.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K4-525AXSP08	189.9	295.1	226.1	253.5	-	189.8	292.5	224.8	251.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K4-532AXSP08	178.1	279.6	213.1	240.1	467.4	178.2	277.2	212	238.2	460.7	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K4-625AXSP08	202.9	312.4	240.8	269.4	512.1	202.8	309.5	239.2	267.2	504.4	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K4-632AXSP08	192.8	300.7	230.4	258.5	497.4	192.9	297.9	229	256.4	489.7	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K5-425AXSP08	170.7	269	204.7	230.6	-	171	266.8	203.5	228.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K5-432AXSP08	158.1	251	190.1	214.7	-	158.4	248.8	189.2	213.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K5-525AXSP08	189.9	295.1	226.1	253.5	-	189.8	292.5	224.8	251.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K5-532AXSP08	178.1	279.6	213.1	240.1	467.4	178.2	277.2	212	238.2	460.7	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K5-625AXSP08	202.9	312.4	240.8	269.4	512.1	202.8	309.5	239.2	267.2	504.4	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K5-632AXSP08	192.8	300.7	230.4	258.5	497.4	192.9	297.9	229	256.4	489.7	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K8-425AXSP08	170.7	269	204.7	230.6	-	171	266.8	203.5	228.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K8-432AXSP08	158.1	251	190.1	214.7	-	158.4	248.8	189.2	213.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK370K8-525AXSP08	189.9	295.1	226.1	253.5	-	189.8	292.5	224.8	251.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K8-532AXSP08	178.1	279.6	213.1	240.1	467.4	178.2	277.2	212	238.2	460.7	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK370K8-625AXSP08	202.9	312.4	240.8	269.4	512.1	202.8	309.5	239.2	267.2	504.4	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK370K8-632AXSP08	192.8	300.7	230.4	258.5	497.4	192.9	297.9	229	256.4	489.7	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400B3-425AXSP08	172.8	272.1	206.9	233.2	-	173	270.1	205.8	231.4	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400B3-432AXSP08	160	254.2	192.4	217.3	-	160.4	252.1	191.5	215.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400B3-525AXSP08	191.7	298.1	228	256	-	191.7	295.6	226.8	254.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400B3-532AXSP08	180.2	283	215.6	242.5	-	180.4	280.4	214.7	240.9	466.2	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400B3-625AXSP08	204.4	314.7	242.2	271	515.9	204.5	312.1	241.2	269.1	508.7	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400B3-632AXSP08	194.6	303.7	232.7	261.1	501.9	194.8	301	231.4	259	494.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400C3-425AXSP08	177.3	279.5	212.7	239.4	-	177.3	277.3	211.5	237.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400C3-432AXSP08	164	260.2	197.4	222.7	-	164.2	258.5	196.2	221.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400C3-432AXSP08	197.6	307.6	235	264	-	197.5	305	233.8	262	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400C3-532AXSP08	185.3	291.1	221.5	249.3	-	185.1	288.6	220.4	247.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400C3-625AXSP08	211.6	325.8	250.9	280.8	535.2	211.6	322.9	249.3	278.5	527.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400C3-632AXSP08	200.8	312.8	239.8	269.2	518.8	201	310.5	238.4	267.1	510.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400C9-425AXSP08	177.3	279.5	212.7	239.4	-	177.3	277.3	211.5	237.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400C9-432AXSP08	164	260.2	197.4	222.7	-	164.2	258.5	196.2	221.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400C9-525AXSP08	197.6	307.6	235	264	-	197.5	305	233.8	262	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400C9-532AXSP08	185.3	291.1	221.5	249.3	-	185.1	288.6	220.4	247.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400K3-425AXSP08	178.1	279.6	213.1	240.1	467.4	178.2	277.2	212	238.2	460.7	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK400K3-432AXSP08	202.9	312.4	240.8	269.4	512.1	202.8	309.5	239.2	267.2	504.4	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400K3-625AXSP08	192.8	300.7	230.4	258.5	497.4	192.9	297.9	229	256.4	489.7	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK400K9-425AXSP08	170.7	269	204.7	230.6	-	171	266.8	203.5	228.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400K9-432AXSP08	158.1	251	190.1	214.7	-	158.4	248.8	189.2	213.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK400K9-525AXSP08	189.9	295.1	226.1	253.5	-	189.8													

EAW-VD1553PK550C4-625AXSP08	238.5	368.9	283.1	317.3	-	238.8	366	281.7	315.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C4-632AXSP08	225.7	352.4	269.1	302.5	-	226.2	349.6	267.9	300.5	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C5-425AXSP08	198.1	313.5	237.8	268.1	-	198.1	310.9	236.7	266.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550C5-432AXSP08	182.4	290.8	219.7	248.5	-	182.6	288.7	218.7	247.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550C5-525AXSP08	221.3	346.5	264.4	297.1	-	221.5	343.8	262.9	295.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550C5-532AXSP08	206.8	326	248.1	279.2	-	206.9	323.6	246.8	277.5	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550C5-625AXSP08	238.5	368.9	283.1	317.3	-	238.8	366	281.7	315.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C5-632AXSP08	225.7	352.4	269.1	302.5	-	226.2	349.6	267.9	300.5	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C8-425AXSP08	198.1	313.5	237.8	268.1	-	198.1	310.9	236.7	266.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550C8-432AXSP08	182.4	290.8	219.7	248.5	-	182.6	288.7	218.7	247.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550C8-525AXSP08	221.3	346.5	264.4	297.1	-	221.5	343.8	262.9	295.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550C8-532AXSP08	206.8	326	248.1	279.2	-	206.9	323.6	246.8	277.5	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550C8-625AXSP08	238.5	368.9	283.1	317.3	-	238.8	366	281.7	315.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C8-632AXSP08	225.7	352.4	269.1	302.5	-	226.2	349.6	267.9	300.5	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C9-425AXSP08	198.1	313.5	237.8	268.1	-	198.1	310.9	236.7	266.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550C9-432AXSP08	182.4	290.8	219.7	248.5	-	182.6	288.7	218.7	247.1	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550C9-525AXSP08	221.3	346.5	264.4	297.1	-	221.5	343.8	262.9	295.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550C9-532AXSP08	206.8	326	248.1	279.2	-	206.9	323.6	246.8	277.5	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550C9-625AXSP08	238.5	368.9	283.1	317.3	-	238.8	366	281.7	315.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550C9-632AXSP08	225.7	352.4	269.1	302.5	-	226.2	349.6	267.9	300.5	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K2-425AXSP08	189.7	299.8	227.4	256.3	-	189.6	297.3	226.4	254.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K2-432AXSP08	175	278.8	210.8	238.1	-	175.4	276.8	210.1	236.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K2-525AXSP08	211	329.5	251.5	282.8	-	211.2	327.1	250.5	281.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K2-532AXSP08	197.8	311.5	237.1	267.1	-	198.3	309.2	235.9	265.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K2-625AXSP08	226.6	349.7	268.8	301.1	-	226.8	346.9	267.4	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K2-632AXSP08	214.9	335.3	256.5	288.1	557.1	215.4	332.7	255.3	286.2	549.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K3-425AXSP08	189.7	299.8	227.4	256.3	-	189.6	297.3	226.4	254.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K3-432AXSP08	175	278.8	210.8	238.1	-	175.4	276.8	210.1	236.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K3-525AXSP08	211	329.5	251.5	282.8	-	211.2	327.1	250.5	281.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K3-532AXSP08	197.8	311.5	237.1	267.1	-	198.3	309.2	235.9	265.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K3-625AXSP08	226.6	349.7	268.8	301.1	-	226.8	346.9	267.4	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K3-632AXSP08	214.9	335.3	256.5	288.1	557.1	215.4	332.7	255.3	286.2	549.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K4-425AXSP08	189.7	299.8	227.4	256.3	-	189.6	297.3	226.4	254.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K4-432AXSP08	175	278.8	210.8	238.1	-	175.4	276.8	210.1	236.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K4-525AXSP08	211	329.5	251.5	282.8	-	211.2	327.1	250.5	281.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K4-532AXSP08	197.8	311.5	237.1	267.1	-	198.3	309.2	235.9	265.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K4-625AXSP08	226.6	349.7	268.8	301.1	-	226.8	346.9	267.4	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K4-632AXSP08	214.9	335.3	256.5	288.1	557.1	215.4	332.7	255.3	286.2	549.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K5-425AXSP08	189.7	299.8	227.4	256.3	-	189.6	297.3	226.4	254.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K5-432AXSP08	175	278.8	210.8	238.1	-	175.4	276.8	210.1	236.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K5-525AXSP08	211	329.5	251.5	282.8	-	211.2	327.1	250.5	281.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K5-532AXSP08	197.8	311.5	237.1	267.1	-	198.3	309.2	235.9	265.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K5-625AXSP08	226.6	349.7	268.8	301.1	-	226.8	346.9	267.4	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K5-632AXSP08	214.9	335.3	256.5	288.1	557.1	215.4	332.7	255.3	286.2	549.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K8-425AXSP08	189.7	299.8	227.4	256.3	-	189.6	297.3	226.4	254.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K8-432AXSP08	175	278.8	210.8	238.1	-	175.4	276.8	210.1	236.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K8-525AXSP08	211	329.5	251.5	282.8	-	211.2	327.1	250.5	281.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K8-532AXSP08	197.8	311.5	237.1	267.1	-	198.3	309.2	235.9	265.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K8-625AXSP08	226.6	349.7	268.8	301.1	-	226.8	346.9	267.4	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K8-632AXSP08	214.9	335.3	256.5	288.1	557.1	215.4	332.7	255.3	286.2	549.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K9-425AXSP08	189.7	299.8	227.4	256.3	-	189.6	297.3	226.4	254.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K9-432AXSP08	175	278.8	210.8	238.1	-	175.4	276.8	210.1	236.7	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550K9-525AXSP08	211	329.5	251.5	282.8	-	211.2	327.1	250.5	281.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K9-532AXSP08	197.8	311.5	237.1	267.1	-	198.3	309.2	235.9	265.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550K9-625AXSP08	226.6	349.7	268.8	301.1	-	226.8	346.9	267.4	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550K9-632AXSP08	214.9	335.3	256.5	288.1	557.1	215.4	332.7	255.3	286.2	549.2	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550R3-425AXSP08	194.1	307.3	233.3	263	-	194.5	304.9	232.4	261.3	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550R3-432AXSP08	179.3	285.6	216.2	244.2	-	179.6	283.7	215.1	242.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK550R3-525AXSP08	216.2	338.1	257.9	290	-	216.6	335.3	257	288.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550R3-532AXSP08	202.7	319.7	243.1	274	-	203	317.1	242	272.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK550R3-625AXSP08	232.5	358.6	275.4	308.6	-	232.5	355.9	274.2	306.6	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK550R3-632AXSP08	220.5	343.9	262.8	295.4	-	220.6	341.4	261.8	293.5	563.9	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750C2-425AXSP06	197.2	319.3	239.7	272.3	-	199	318.6	240.3	271.7	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD1553PK750C2-432AXSP08	193.8	309.6	233.8	264.4	-	194.2	307.9	233.1	262.9	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750C2-525AXSP08	234.9	367.8	280.5	315.9	-	235.3	365.7	279.4	313.9	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750C2-532AXSP																			

EAW-VD1553PK750K2-532AXSP08	212.2	335.1	254.8	287.4	-	212.9	333.4	254	285.7	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K2-625AXSP08	243.4	376.7	288.9	323.9	-	244	374.2	287.9	322.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K2-632AXSP08	231.2	360.9	275.8	309.7	-	231.4	358.6	274.5	308	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K3-425AXSP06	190.8	309	232	263.4	-	192.7	308.4	232.6	263.2	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD1553PK750K3-432AXSP08	187.9	300	226.5	256.2	-	188.2	297.7	225.8	255	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750K3-525AXSP08	226.9	354.6	270.8	304.3	-	227.2	352.5	269.7	302.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K3-532AXSP08	212.2	335.1	254.8	287.4	-	212.9	333.4	254	285.7	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K3-625AXSP08	243.4	376.7	288.9	323.9	-	244	374.2	287.9	322.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K3-632AXSP08	231.2	360.9	275.8	309.7	-	231.4	358.6	274.5	308	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K4-425AXSP06	190.8	309	232	263.4	-	192.7	308.4	232.6	263.2	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD1553PK750K4-432AXSP08	187.9	300	226.5	256.2	-	188.2	297.7	225.8	255	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750K4-525AXSP08	226.9	354.6	270.8	304.3	-	227.2	352.5	269.7	302.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K4-532AXSP08	212.2	335.1	254.8	287.4	-	212.9	333.4	254	285.7	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K4-625AXSP08	243.4	376.7	288.9	323.9	-	244	374.2	287.9	322.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K4-632AXSP08	231.2	360.9	275.8	309.7	-	231.4	358.6	274.5	308	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K9-425AXSP06	190.8	309	232	263.4	-	192.7	308.4	232.6	263.2	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD1553PK750K9-432AXSP08	187.9	300	226.5	256.2	-	188.2	297.7	225.8	255	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750K9-525AXSP08	226.9	354.6	270.8	304.3	-	227.2	352.5	269.7	302.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K9-532AXSP08	212.2	335.1	254.8	287.4	-	212.9	333.4	254	285.7	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K9-625AXSP08	243.4	376.7	288.9	323.9	-	244	374.2	287.9	322.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K9-632AXSP08	231.2	360.9	275.8	309.7	-	231.4	358.6	274.5	308	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K8-432AXSP08	187.9	300	226.5	256.2	-	188.2	297.7	225.8	255	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750K8-525AXSP08	226.9	354.6	270.8	304.3	-	227.2	352.5	269.7	302.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K8-532AXSP08	212.2	335.1	254.8	287.4	-	212.9	333.4	254	285.7	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K8-625AXSP08	243.4	376.7	288.9	323.9	-	244	374.2	287.9	322.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K8-632AXSP08	231.2	360.9	275.8	309.7	-	231.4	358.6	274.5	308	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K9-425AXSP06	190.8	309	232	263.4	-	192.7	308.4	232.6	263.2	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD1553PK750K9-432AXSP08	187.9	300	226.5	256.2	-	188.2	297.7	225.8	255	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750K9-525AXSP08	226.9	354.6	270.8	304.3	-	227.2	352.5	269.7	302.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K9-532AXSP08	212.2	335.1	254.8	287.4	-	212.9	333.4	254	285.7	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750K9-625AXSP08	243.4	376.7	288.9	323.9	-	244	374.2	287.9	322.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750K9-632AXSP08	231.2	360.9	275.8	309.7	-	231.4	358.6	274.5	308	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750R3-425AXSP08	199.4	315.7	233.3	270	-	199.8	313.7	238.8	268.6	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750R3-432AXSP08	184.3	293.8	222	251	-	184.7	292	221.2	249.8	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD1553PK750R3-525AXSP08	221.7	346.6	264.5	297.6	-	222.3	344.5	263.8	296.1	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750R3-532AXSP08	208	328	249.2	280.9	-	208.6	325.7	248.3	279.3	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD1553PK750R3-625AXSP08	238	368	282.4	316.5	-	238.2	365	281.3	314.7	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553PK750R3-632AXSP08	226	352.9	269.4	302.9	-	226.5	350.1	268.6	301.3	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD1553ZB370C2-425AXSP08	190.7	302.2	229.6	259	507.9	191.2	299.6	228.5	257.1	500.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C2-432AXSP08	175.7	281.2	213	240.8	476.1	176.3	279	211.9	238.9	469.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C2-525AXSP08	209.4	329.3	251.6	282.9	546.9	209.8	326.2	250	280.5	538.8	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C2-532AXSP08	195.6	311.1	236.4	266.3	521.1	196	308.2	235.1	264.2	512.5	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C2-625AXSP12	240.6	363.3	282	313.9	-	238.9	358.1	278.7	310.1	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C2-632AXSP12	228.6	348.4	269.2	300.7	-	226.9	343.8	266	296.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C4-425AXSP08	190.7	302.2	229.6	259	507.9	191.2	299.6	228.5	257.1	500.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C4-432AXSP08	175.7	281.2	213	240.8	476.1	176.3	279	211.9	238.9	469.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C4-525AXSP08	209.4	329.3	251.6	282.9	546.9	209.8	326.2	250	280.5	538.8	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C4-532AXSP08	195.6	311.1	236.4	266.3	521.1	196	308.2	235.1	264.2	512.5	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C4-625AXSP12	240.6	363.3	282	313.9	-	238.9	358.1	278.7	310.1	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C4-632AXSP12	228.6	348.4	269.2	300.7	-	226.9	343.8	266	296.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C5-425AXSP08	190.7	302.2	229.6	259	507.9	191.2	299.6	228.5	257.1	500.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C5-432AXSP08	175.7	281.2	213	240.8	476.1	176.3	279	211.9	238.9	469.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C5-525AXSP08	209.4	329.3	251.6	282.9	546.9	209.8	326.2	250	280.5	538.8	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C5-532AXSP08	195.6	311.1	236.4	266.3	521.1	196	308.2	235.1	264.2	512.5	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C5-625AXSP12	240.6	363.3	282	313.9	-	238.9	358.1	278.7	310.1	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C5-632AXSP12	228.6	348.4	269.2	300.7	-	226.9	343.8	266	296.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C8-425AXSP08	190.7	302.2	229.6	259	507.9	191.2	299.6	228.5	257.1	500.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C8-432AXSP08	175.7	281.2	213	240.8	476.1	176.3	279	211.9	238.9	469.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370C8-525AXSP08	209.4	329.3	251.6	282.9	546.9	209.8	326.2	250	280.5	538.8	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C8-532AXSP08	195.6	311.1	236.4	266.3	521.1	196	308.2	235.1	264.2	512.5	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB370C8-625AXSP12	240.6	363.3	282	313.9	-	238.9	358.1	278.7	310.1	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370C8-632AXSP12	228.6	348.4	269.2	300.7	-	226.9	343.8	266	296.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB370K2-425AXSP08	183.4	290.6	221.2	249.3	488.4	184	288.2	220.1	247.5	480.7	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370K2-432AXSP08	169.7	271.4	205.6	232.2	458.8	169.9	269.3	204.5	230.4	452.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB370K2-525AXSP08	200.9	315.9	241.3	271.6	524.1	201.3	312.8	240.1	269.2	516.3	3								

EAW-VD1553ZB400C9-525AXSP08	209.4	329.3	251.6	282.9	546.9	209.8	326.2	250	280.5	538.8	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB400C9-532AXSP08	195.6	311.1	236.4	266.3	521.1	196	308.2	235.1	264.2	512.5	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB400C9-625AXSP12	240.6	363.3	282	313.9	-	238.9	358.1	278.7	310.1	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400C9-632AXSP12	228.6	348.4	269.2	300.7	-	226.9	343.8	266	296.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400K3-425AXSP08	183.4	290.6	221.2	249.3	488.4	184	288.2	220.1	247.5	480.7	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB400K3-432AXSP08	169.7	271.4	205.6	232.2	458.8	169.9	269.3	204.5	230.4	452.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB400K3-525AXSP08	200.9	315.9	241.3	271.6	524.1	201.3	312.8	240.1	269.2	516.3	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB400K3-532AXSP12	199.6	307.7	236.4	264.5	-	198.4	303.5	233.8	261.5	-	248	31.1	3"	198	23.8	2"	298	43.5	3"
EAW-VD1553ZB400K3-625AXSP12	230.9	347.9	269.9	300.8	-	229	342.9	267.1	296.7	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400K3-632AXSP12	219.5	334.1	258.4	288.5	-	218.1	329.7	255.4	284.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400K9-425AXSP08	183.4	290.6	221.2	249.3	488.4	184	288.2	220.1	247.5	480.7	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB400K9-432AXSP08	169.7	271.4	205.6	232.2	458.8	169.9	269.3	204.5	230.4	452.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB400K9-525AXSP08	200.9	315.9	241.3	271.6	524.1	201.3	312.8	240.1	269.2	516.3	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB400K9-532AXSP12	199.6	307.7	236.4	264.5	-	198.4	303.5	233.8	261.5	-	248	31.1	3"	198	23.8	2"	298	43.5	3"
EAW-VD1553ZB400K9-625AXSP12	230.9	347.9	269.9	300.8	-	229	342.9	267.1	296.7	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400K9-632AXSP12	219.5	334.1	258.4	288.5	-	218.1	329.7	255.4	284.6	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400K9-632AXSP12	187.3	296.6	225.5	254.3	498.9	187.6	294.2	224.6	252.6	491.1	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB400R3-432AXSP08	173	277	209.7	236.9	468.8	173.7	275.1	209.1	235.6	462.3	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB400R3-525AXSP08	205	322.6	246.3	276.9	535.5	205.5	319.6	245.2	274.6	527.1	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB400R3-532AXSP12	203.5	314.1	241.1	270.3	-	202.4	309.9	238.6	266.9	-	248	31.1	3"	198	23.8	2"	298	43.5	3"
EAW-VD1553ZB400R3-625AXSP12	235.2	355	275.4	306.9	-	233.7	350.1	272.5	302.8	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB400R3-632AXSP12	224.1	341.3	263.4	294.2	-	222.5	336.5	260.8	290.7	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB550B3-425AXSP08	205	324.7	246.4	278.2	-	205.2	322.4	245.6	276.1	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550B3-432AXSP08	188.8	302.2	228.6	258.3	-	189.6	300.3	227.8	256.6	505.8	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550B3-525AXSP08	224.9	353.4	269.8	303.6	588.9	225.5	350.5	268.5	301.1	580.9	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550B3-532AXSP08	210.1	333.9	253.8	286.2	560.7	210.9	331.4	252.5	284	553.1	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550B3-625AXSP08	242.2	377.9	289.7	325.2	621.6	243.2	374.3	288.6	322.9	612.7	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550B3-632AXSP12	244.7	374.5	288.8	322.8	-	243.3	369.6	285.8	318.9	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB550C2-425AXSP08	214.1	340	257.5	291	-	214.7	337.4	256.6	288.7	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C2-432AXSP08	196.9	315.5	238.2	269.3	-	197.3	312.9	237.3	267.5	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C2-525AXSP08	236.6	372	283.5	319.3	620.8	237	368.8	282	316.9	612	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C2-532AXSP08	220	349.9	265.6	299.7	588.6	220.8	346.6	264.4	297.1	579.4	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C2-625AXSP08	256.3	399.6	306.7	344	659.6	257	395.8	304.7	341.1	649.4	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C2-632AXSP08	241.4	381.1	290.8	327.1	633.8	242.1	377.7	289.1	324.5	624.7	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C3-425AXSP08	214.1	340	257.5	291	-	214.7	337.4	256.6	288.7	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C3-432AXSP08	196.9	315.5	238.2	269.3	-	197.3	312.9	237.3	267.5	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C3-525AXSP08	236.6	372	283.5	319.3	620.8	237	368.8	282	316.9	612	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C3-532AXSP08	220	349.9	265.6	299.7	588.6	220.8	346.6	264.4	297.1	579.4	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C3-625AXSP08	256.3	399.6	306.7	344	659.6	257	395.8	304.7	341.1	649.4	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C3-632AXSP08	241.4	381.1	290.8	327.1	633.8	242.1	377.7	289.1	324.5	624.7	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C4-425AXSP08	214.1	340	257.5	291	-	214.7	337.4	256.6	288.7	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C4-432AXSP08	196.9	315.5	238.2	269.3	-	197.3	312.9	237.3	267.5	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C4-525AXSP08	236.6	372	283.5	319.3	620.8	237	368.8	282	316.9	612	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C4-532AXSP08	220	349.9	265.6	299.7	588.6	220.8	346.6	264.4	297.1	579.4	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C4-625AXSP08	256.3	399.6	306.7	344	659.6	257	395.8	304.7	341.1	649.4	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C4-632AXSP08	241.4	381.1	290.8	327.1	633.8	242.1	377.7	289.1	324.5	624.7	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C5-425AXSP08	214.1	340	257.5	291	-	214.7	337.4	256.6	288.7	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C5-432AXSP08	196.9	315.5	238.2	269.3	-	197.3	312.9	237.3	267.5	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C5-525AXSP08	236.6	372	283.5	319.3	620.8	237	368.8	282	316.9	612	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C5-532AXSP08	220	349.9	265.6	299.7	588.6	220.8	346.6	264.4	297.1	579.4	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C5-625AXSP08	256.3	399.6	306.7	344	659.6	257	395.8	304.7	341.1	649.4	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C5-632AXSP08	241.4	381.1	290.8	327.1	633.8	242.1	377.7	289.1	324.5	624.7	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C8-425AXSP08	214.1	340	257.5	291	-	214.7	337.4	256.6	288.7	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C8-432AXSP08	196.9	315.5	238.2	269.3	-	197.3	312.9	237.3	267.5	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C8-525AXSP08	236.6	372	283.5	319.3	620.8	237	368.8	282	316.9	612	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C8-532AXSP08	220	349.9	265.6	299.7	588.6	220.8	346.6	264.4	297.1	579.4	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C8-625AXSP08	256.3	399.6	306.7	344	659.6	257	395.8	304.7	341.1	649.4	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C8-632AXSP08	241.4	381.1	290.8	327.1	633.8	242.1	377.7	289.1	324.5	624.7	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C9-425AXSP08	214.1	340	257.5	291	-	214.7	337.4	256.6	288.7	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C9-432AXSP08	196.9	315.5	238.2	269.3	-	197.3	312.9	237.3	267.5	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550C9-525AXSP08	236.6	372	283.5	319.3	620.8	237	368.8	282	316.9	612	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C9-532AXSP08	220	349.9	265.6	299.7	588.6	220.8	346.6	264.4	297.1	579.4	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550C9-625AXSP08	256.3	399.6	306.7	344	659.6	257	395.8	304.7	341.1	649.4	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550C9-632AXSP08																			

EAW-VD1553ZB550R3-432AXSP08	194.6	311.5	235.3	266	-	195.1	309.2	234.6	264.4	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB550R3-525AXSP08	232.3	364.9	278.3	312.8	608.5	232.5	362	277	310.7	599.6	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550R3-532AXSP08	216.5	344.1	261.4	294.8	578.5	217.1	341.1	260	292.6	570	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB550R3-625AXSP08	250.6	390.4	299.8	336.2	644.1	251.2	387.2	298.2	333.8	634.1	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB550R3-632AXSP12	252.4	386.2	298	333.2	-	251	381.7	294.9	329.1	-	304	31.7	3"	244	20.9	3"	365	44.4	3"
EAW-VD1553ZB750C2-425AXSP08	229	364.8	275.9	312.2	-	229.7	362.1	275	310.3	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C2-432AXSP08	211.1	338	255.1	289	-	211.8	335.8	254.2	287	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C2-525AXSP08	253.5	398.7	303.5	342.2	-	254.1	396	302.6	339.8	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C2-532AXSP08	235.9	375	284.2	321.1	-	236.9	372	283.6	319	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C2-625AXSP08	274.6	428.1	327.9	368.2	708.6	275.1	424.8	326.4	365.7	697.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C2-632AXSP08	258.8	408.3	311.2	350.4	681.2	259.7	405.3	310	348.3	671.6	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C3-425AXSP08	229	364.8	275.9	312.2	-	229.7	362.1	275	310.3	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C3-432AXSP08	211.1	338	255.1	289	-	211.8	335.8	254.2	287	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C3-525AXSP08	253.5	398.7	303.5	342.2	-	254.1	396	302.6	339.8	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C3-532AXSP08	235.9	375	284.2	321.1	-	236.9	372	283.6	319	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C3-625AXSP08	274.6	428.1	327.9	368.2	708.6	275.1	424.8	326.4	365.7	697.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C3-632AXSP08	258.8	408.3	311.2	350.4	681.2	259.7	405.3	310	348.3	671.6	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C4-425AXSP08	229	364.8	275.9	312.2	-	229.7	362.1	275	310.3	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C4-432AXSP08	211.1	338	255.1	289	-	211.8	335.8	254.2	287	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C4-525AXSP08	253.5	398.7	303.5	342.2	-	254.1	396	302.6	339.8	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C4-532AXSP08	235.9	375	284.2	321.1	-	236.9	372	283.6	319	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C4-625AXSP08	274.6	428.1	327.9	368.2	708.6	275.1	424.8	326.4	365.7	697.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C4-632AXSP08	258.8	408.3	311.2	350.4	681.2	259.7	405.3	310	348.3	671.6	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C5-425AXSP08	229	364.8	275.9	312.2	-	229.7	362.1	275	310.3	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C5-432AXSP08	211.1	338	255.1	289	-	211.8	335.8	254.2	287	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C5-525AXSP08	253.5	398.7	303.5	342.2	-	254.1	396	302.6	339.8	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C5-532AXSP08	235.9	375	284.2	321.1	-	236.9	372	283.6	319	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C5-625AXSP08	274.6	428.1	327.9	368.2	708.6	275.1	424.8	326.4	365.7	697.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C5-632AXSP08	258.8	408.3	311.2	350.4	681.2	259.7	405.3	310	348.3	671.6	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C8-425AXSP08	229	364.8	275.9	312.2	-	229.7	362.1	275	310.3	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C8-432AXSP08	211.1	338	255.1	289	-	211.8	335.8	254.2	287	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C8-525AXSP08	253.5	398.7	303.5	342.2	-	254.1	396	302.6	339.8	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C8-532AXSP08	235.9	375	284.2	321.1	-	236.9	372	283.6	319	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C8-625AXSP08	274.6	428.1	327.9	368.2	708.6	275.1	424.8	326.4	365.7	697.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C8-632AXSP08	258.8	408.3	311.2	350.4	681.2	259.7	405.3	310	348.3	671.6	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C9-425AXSP08	229	364.8	275.9	312.2	-	229.7	362.1	275	310.3	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C9-432AXSP08	211.1	338	255.1	289	-	211.8	335.8	254.2	287	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750C9-525AXSP08	253.5	398.7	303.5	342.2	-	254.1	396	302.6	339.8	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C9-532AXSP08	235.9	375	284.2	321.1	-	236.9	372	283.6	319	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750C9-625AXSP08	274.6	428.1	327.9	368.2	708.6	275.1	424.8	326.4	365.7	697.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750C9-632AXSP08	258.8	408.3	311.2	350.4	681.2	259.7	405.3	310	348.3	671.6	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K2-425AXSP08	222.1	352.9	267.3	301.7	-	222.7	350.2	266.3	299.9	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K2-432AXSP08	204.7	327.9	247.5	280.1	-	205.4	325.3	246.6	278.2	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K2-525AXSP08	244.7	384.8	293.3	330	-	245.5	382	291.8	328	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K2-532AXSP08	228.2	362.6	274.8	310.3	610.8	228.7	359.7	274.1	308.2	602.2	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K2-625AXSP08	264.5	412.2	315.7	354.2	680.8	265	408.7	314.8	352	670.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K2-632AXSP08	249.5	394.1	300.8	338	656.8	250.6	391	299.5	335.8	647.3	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K3-425AXSP08	222.1	352.9	267.3	301.7	-	222.7	350.2	266.3	299.9	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K3-432AXSP08	204.7	327.9	247.5	280.1	-	205.4	325.3	246.6	278.2	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K3-525AXSP08	244.7	384.8	293.3	330	-	245.5	382	291.8	328	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K3-532AXSP08	228.2	362.6	274.8	310.3	610.8	228.7	359.7	274.1	308.2	602.2	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K3-625AXSP08	264.5	412.2	315.7	354.2	680.8	265	408.7	314.8	352	670.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K3-632AXSP08	249.5	394.1	300.8	338	656.8	250.6	391	299.5	335.8	647.3	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K4-425AXSP08	222.1	352.9	267.3	301.7	-	222.7	350.2	266.3	299.9	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K4-432AXSP08	204.7	327.9	247.5	280.1	-	205.4	325.3	246.6	278.2	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K4-525AXSP08	244.7	384.8	293.3	330	-	245.5	382	291.8	328	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K4-532AXSP08	228.2	362.6	274.8	310.3	610.8	228.7	359.7	274.1	308.2	602.2	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K4-625AXSP08	264.5	412.2	315.7	354.2	680.8	265	408.7	314.8	352	670.9	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K4-632AXSP08	249.5	394.1	300.8	338	656.8	250.6	391	299.5	335.8	647.3	451	23.8	3"	361	15.7	3"	541	29.7	4"
EAW-VD1553ZB750K5-425AXSP08	222.1	352.9	267.3	301.7	-	222.7	350.2	266.3	299.9	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K5-432AXSP08	204.7	327.9	247.5	280.1	-	205.4	325.3	246.6	278.2	-	304	21.7	3"	244	14.3	3"	365	30.4	3"
EAW-VD1553ZB750K5-525AXSP08	244.7	384.8	293.3	330	-	245.5	382	291.8	328	-	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K5-532AXSP08	228.2	362.6	274.8	310.3	610.8	228.7	359.7	274.1	308.2	602.2	372	22.6	3"	298	14.9	3"	446	31.7	3"
EAW-VD1553ZB750K5-625AXSP08	264.5	412.2	315.7	354.2	680.8	265	408.7	314.8	352	670.9	451	23.8	3"	361	15.7	3"	541	29.7	4"

EAW-VD1553ZK370C5-425AXSP08	202.8	317.7	242.2	272.4	-	202.3	314.1	240.3	270	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370C5-432AXSP08	187	295.9	224.6	253.5	497.8	186.6	292.8	223.1	251.1	490.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370C5-525AXSP08	222.7	346.2	265.3	297.5	571.7	222.3	341.9	263.2	294.5	561.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370C5-532AXSP08	208	326.6	249.4	280.5	544.2	207.7	323.2	247.6	277.5	534.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370C5-625AXSP08	240.2	370	285.1	319.2	603.9	239.8	365.3	282.7	315.4	593	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK370C5-632AXSP12	240.8	365	282.6	315.4	-	238.6	359.3	278.9	310.7	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370C8-425AXSP08	202.8	317.7	242.2	272.4	-	202.3	314.1	240.3	270	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370C8-432AXSP08	187	295.9	224.6	253.5	497.8	186.6	292.8	223.1	251.1	490.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370C8-525AXSP08	222.7	346.2	265.3	297.5	571.7	222.3	341.9	263.2	294.5	561.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370C8-532AXSP08	208	326.6	249.4	280.5	544.2	207.7	323.2	247.6	277.5	534.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370C8-625AXSP08	240.2	370	285.1	319.2	603.9	239.8	365.3	282.7	315.4	593	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK370C8-632AXSP12	240.8	365	282.6	315.4	-	238.6	359.3	278.9	310.7	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370K2-425AXSP08	195	306	233.2	262.5	-	194.9	302.6	231.8	259.9	502.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370K2-432AXSP08	180.4	285.9	217	244.7	480.3	180.3	282.9	215.5	242.5	472.9	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370K2-525AXSP08	213.7	332.2	254.8	285.7	548	213.4	328.2	252.8	282.9	538.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370K2-532AXSP08	200	314.4	240	269.9	523.3	200	311.2	238.4	267.4	514.4	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370K2-625AXSP12	243.1	364.2	283.8	315.2	-	240.9	358.6	280.1	310.6	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370K2-632AXSP12	231.6	350.2	271.4	302.4	-	229.3	344.8	267.9	298	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370K4-425AXSP08	195	306	233.2	262.5	-	194.9	302.6	231.8	259.9	502.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370K4-432AXSP08	180.4	285.9	217	244.7	480.3	180.3	282.9	215.5	242.5	472.9	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370K4-525AXSP08	213.7	332.2	254.8	285.7	548	213.4	328.2	252.8	282.9	538.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370K4-532AXSP08	200	314.4	240	269.9	523.3	200	311.2	238.4	267.4	514.4	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370K4-625AXSP12	243.1	364.2	283.8	315.2	-	240.9	358.6	280.1	310.6	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370K4-632AXSP12	231.6	350.2	271.4	302.4	-	229.3	344.8	267.9	298	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370K8-425AXSP08	195	306	233.2	262.5	-	194.9	302.6	231.8	259.9	502.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370K8-432AXSP08	180.4	285.9	217	244.7	480.3	180.3	282.9	215.5	242.5	472.9	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK370K8-525AXSP08	213.7	332.2	254.8	285.7	548	213.4	328.2	252.8	282.9	538.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370K8-532AXSP08	200	314.4	240	269.9	523.3	200	311.2	238.4	267.4	514.4	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK370K8-625AXSP12	243.1	364.2	283.8	315.2	-	240.9	358.6	280.1	310.6	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK370K8-632AXSP12	231.6	350.2	271.4	302.4	-	229.3	344.8	267.9	298	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400B3-425AXSP08	197.8	310.1	236.6	266.4	-	197.7	307.1	234.8	263.7	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400B3-432AXSP08	182.8	289.4	219.9	248.1	487.2	182.7	286.8	218.4	245.8	479.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400B3-525AXSP08	216.7	337	258.4	289.7	556.1	216.4	333	256.5	287	546.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400B3-532AXSP08	203.1	319	243.4	273.8	530.5	202.9	315.4	241.8	271.3	522.3	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400B3-625AXSP08	233.6	359.5	277.2	310.2	585.8	232.9	355	274.5	306.6	575.3	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK400B3-632AXSP12	234.6	355.3	275.3	306.8	-	232.6	349.9	271.8	302.4	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400C3-425AXSP08	202.8	317.7	242.2	272.4	-	202.3	314.1	240.3	270	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400C3-432AXSP08	187	295.9	224.6	253.5	497.8	186.6	292.8	223.1	251.1	490.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400C3-525AXSP08	222.7	346.2	265.3	297.5	571.7	222.3	341.9	263.2	294.5	561.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400C3-532AXSP08	208	326.6	249.4	280.5	544.2	207.7	323.2	247.6	277.5	534.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400C3-625AXSP08	240.2	370	285.1	319.2	603.9	239.8	365.3	282.7	315.4	593	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK400C3-632AXSP12	240.8	365	282.6	315.4	-	238.6	359.3	278.9	310.7	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400C9-425AXSP08	202.8	317.7	242.2	272.4	-	202.3	314.1	240.3	270	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400C9-432AXSP08	187	295.9	224.6	253.5	497.8	186.6	292.8	223.1	251.1	490.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400C9-525AXSP08	222.7	346.2	265.3	297.5	571.7	222.3	341.9	263.2	294.5	561.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400C9-532AXSP08	208	326.6	249.4	280.5	544.2	207.7	323.2	247.6	277.5	534.7	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400C9-625AXSP08	240.2	370	285.1	319.2	603.9	239.8	365.3	282.7	315.4	593	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK400C9-632AXSP12	240.8	365	282.6	315.4	-	238.6	359.3	278.9	310.7	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400K3-425AXSP08	195	306	233.2	262.5	-	194.9	302.6	231.8	259.9	502.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400K3-432AXSP08	180.4	285.9	217	244.7	480.3	180.3	282.9	215.5	242.5	472.9	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400K3-525AXSP08	213.7	332.2	254.8	285.7	548	213.4	328.2	252.8	282.9	538.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400K3-532AXSP08	200	314.4	240	269.9	523.3	200	311.2	238.4	267.4	514.4	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400K3-625AXSP12	243.1	364.2	283.8	315.2	-	240.9	358.6	280.1	310.6	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400K3-632AXSP12	231.6	350.2	271.4	302.4	-	229.3	344.8	267.9	298	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400K9-425AXSP08	195	306	233.2	262.5	-	194.9	302.6	231.8	259.9	502.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400K9-432AXSP08	180.4	285.9	217	244.7	480.3	180.3	282.9	215.5	242.5	472.9	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK400K9-525AXSP08	213.7	332.2	254.8	285.7	548	213.4	328.2	252.8	282.9	538.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400K9-532AXSP08	200	314.4	240	269.9	523.3	200	311.2	238.4	267.4	514.4	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK400K9-625AXSP12	243.1	364.2	283.8	315.2	-	240.9	358.6	280.1	310.6	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK400K9-632AXSP12	231.6	350.2	271.4	302.4	-	229.3	344.8	267.9	298	-	304	34.6	3"	244	22.9	3"	365	48.6	3"
EAW-VD1553ZK500B3-425AXSP08	195	306	233.2	262.5	-	194.9	302.6	231.8	259.9	502.1	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK500B3-432AXSP08	180.4	285.9	217	244.7	480.3	180.3	282.9	215.5	242.5	472.9	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK500B3-525AXSP08	213.7	332.2	254.8	285.7	548	213.4	328.2	252.8	282.9	538.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK500B3-53																			

EAW-VD1553ZK550C5-632AXSP08	257.3	401.4	307.6	345.1	663.6	257.1	396.6	305.3	341.3	653.1	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550C8-425AXSP08	227.6	357.8	272.3	306.8	-	227	354.6	270.5	304	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550C8-432AXSP08	209.5	332.1	251.7	284.2	-	209.3	328.9	250.3	281.8	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550C8-525AXSP08	251.8	391.8	299.9	336.8	-	251.3	387.8	297.8	333.2	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550C8-532AXSP08	234.3	368.3	280.9	316	616.1	234.3	364.8	278.8	312.9	606.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550C8-625AXSP08	273.2	420.9	324.2	362.9	690.3	272.7	416.4	321.7	358.9	678.9	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550C8-632AXSP08	257.3	401.4	307.6	345.1	663.6	257.1	396.6	305.3	341.3	653.1	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550C9-425AXSP08	227.6	357.8	272.3	306.8	-	227	354.6	270.5	304	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550C9-432AXSP08	209.5	332.1	251.7	284.2	-	209.3	328.9	250.3	281.8	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550C9-525AXSP08	251.8	391.8	299.9	336.8	-	251.3	387.8	297.8	333.2	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550C9-532AXSP08	234.3	368.3	280.9	316	616.1	234.3	364.8	278.8	312.9	606.6	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550C9-625AXSP08	273.2	420.9	324.2	362.9	690.3	272.7	416.4	321.7	358.9	678.9	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550C9-632AXSP08	257.3	401.4	307.6	345.1	663.6	257.1	396.6	305.3	341.3	653.1	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K2-425AXSP08	218.4	343.6	261.6	294.5	-	218.3	340.2	259.9	291.9	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K2-432AXSP08	202.1	320.1	242.6	273.7	-	202	316.7	241.4	271.6	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K2-525AXSP08	240.6	374.2	286.4	321.5	619.8	240.3	370.1	284.6	318.8	609.8	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K2-532AXSP08	224.6	353	269.2	303.1	589.6	224.7	349.8	267.7	300.3	580.9	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K2-625AXSP08	260	400.5	308.5	345.1	655.4	259.6	395.9	306.2	341.8	644.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K2-632AXSP08	245.6	383	293.8	329.5	633.2	245.4	379.1	291.4	326.1	622.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K3-425AXSP08	218.4	343.6	261.6	294.5	-	218.3	340.2	259.9	291.9	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K3-432AXSP08	202.1	320.1	242.6	273.7	-	202	316.7	241.4	271.6	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K3-525AXSP08	240.6	374.2	286.4	321.5	619.8	240.3	370.1	284.6	318.8	609.8	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K3-532AXSP08	224.6	353	269.2	303.1	589.6	224.7	349.8	267.7	300.3	580.9	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K3-625AXSP08	260	400.5	308.5	345.1	655.4	259.6	395.9	306.2	341.8	644.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K3-632AXSP08	245.6	383	293.8	329.5	633.2	245.4	379.1	291.4	326.1	622.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K4-425AXSP08	218.4	343.6	261.6	294.5	-	218.3	340.2	259.9	291.9	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K4-432AXSP08	202.1	320.1	242.6	273.7	-	202	316.7	241.4	271.6	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K4-525AXSP08	240.6	374.2	286.4	321.5	619.8	240.3	370.1	284.6	318.8	609.8	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K4-532AXSP08	224.6	353	269.2	303.1	589.6	224.7	349.8	267.7	300.3	580.9	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K4-625AXSP08	260	400.5	308.5	345.1	655.4	259.6	395.9	306.2	341.8	644.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K4-632AXSP08	245.6	383	293.8	329.5	633.2	245.4	379.1	291.4	326.1	622.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K5-425AXSP08	218.4	343.6	261.6	294.5	-	218.3	340.2	259.9	291.9	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K5-432AXSP08	202.1	320.1	242.6	273.7	-	202	316.7	241.4	271.6	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K5-525AXSP08	240.6	374.2	286.4	321.5	619.8	240.3	370.1	284.6	318.8	609.8	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K5-532AXSP08	224.6	353	269.2	303.1	589.6	224.7	349.8	267.7	300.3	580.9	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K5-625AXSP08	260	400.5	308.5	345.1	655.4	259.6	395.9	306.2	341.8	644.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K5-632AXSP08	245.6	383	293.8	329.5	633.2	245.4	379.1	291.4	326.1	622.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K8-425AXSP08	218.4	343.6	261.6	294.5	-	218.3	340.2	259.9	291.9	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K8-432AXSP08	202.1	320.1	242.6	273.7	-	202	316.7	241.4	271.6	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K8-525AXSP08	240.6	374.2	286.4	321.5	619.8	240.3	370.1	284.6	318.8	609.8	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K8-532AXSP08	224.6	353	269.2	303.1	589.6	224.7	349.8	267.7	300.3	580.9	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K8-625AXSP08	260	400.5	308.5	345.1	655.4	259.6	395.9	306.2	341.8	644.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K8-632AXSP08	245.6	383	293.8	329.5	633.2	245.4	379.1	291.4	326.1	622.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K9-425AXSP08	218.4	343.6	261.6	294.5	-	218.3	340.2	259.9	291.9	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K9-432AXSP08	202.1	320.1	242.6	273.7	-	202	316.7	241.4	271.6	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550K9-525AXSP08	240.6	374.2	286.4	321.5	619.8	240.3	370.1	284.6	318.8	609.8	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K9-532AXSP08	224.6	353	269.2	303.1	589.6	224.7	349.8	267.7	300.3	580.9	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550K9-625AXSP08	260	400.5	308.5	345.1	655.4	259.6	395.9	306.2	341.8	644.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550K9-632AXSP08	245.6	383	293.8	329.5	633.2	245.4	379.1	291.4	326.1	622.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550R3-425AXSP08	224.7	353.5	268.9	302.8	-	224.3	350.2	267.3	300.3	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550R3-432AXSP08	207.4	328.7	249.2	281.3	-	207.5	325.9	248.1	279.3	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK550R3-525AXSP08	247.6	385	294.8	331.1	-	247.4	381.4	292.6	327.9	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550R3-532AXSP08	231.1	363.1	277	311.6	607.1	230.9	360	275.2	308.9	598.3	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK550R3-625AXSP08	267.6	412.5	317.5	355.3	676.2	267.2	407.9	315.3	352.1	664.7	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK550R3-632AXSP08	253.1	394.5	302.4	339.3	651.9	252.7	390.2	300	335.9	641.4	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750C2-425AXSP08	244.4	385.9	292.9	330.3	-	244.2	382.3	291.3	327.7	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750C2-432AXSP08	224.9	357.6	270.5	305.9	-	225.1	354.8	269.6	303.3	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750C2-525AXSP08	270.4	422.2	322.4	362.4	-	270	418	320.2	359.2	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750C2-532AXSP08	252.4	397	301.9	340	-	251.9	393.2	300.1	337.2	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750C2-625AXSP08	294.1	453	348.3	390.1	745.8	293.7	448.9	346.2	387	733.7	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750C2-632AXSP08	277.1	431.9	330.6	371.3	717.1	276.9	428	328.7	367.8	705.9	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750C3-425AXSP08	244.4	385.9	292.9	330.3	-	244.2	382.3	291.3	327.7	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750C3-432AXSP08	224.9	357.6	270.5	305.9	-	225.1	354.8	269.6	303.3	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750C3-442AXSP08																			

EAW-VD1553ZK750K3-625AXSP08	283	436.5	335.5	375.6	716.2	282.8	431.8	333.3	372.4	705.3	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K3-632AXSP08	267.1	416.8	319	358.1	690.5	266.9	412.5	317.1	355.2	679.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K4-425AXSP08	236.7	372.9	283.4	319.5	-	236.5	369.6	282	317.1	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K4-432AXSP08	218.4	346.8	262.8	296.9	-	218.4	344.1	261.4	294.5	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K4-525AXSP08	261.4	406.8	311	349.5	-	261	403.4	309.4	346.4	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K4-532AXSP08	244.2	383.4	292	328.7	-	243.8	379.9	290.3	326	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K4-625AXSP08	283	436.5	335.5	375.6	716.2	282.8	431.8	333.3	372.4	705.3	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K4-632AXSP08	267.1	416.8	319	358.1	690.5	266.9	412.5	317.1	355.2	679.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K5-425AXSP08	236.7	372.9	283.4	319.5	-	236.5	369.6	282	317.1	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K5-432AXSP08	218.4	346.8	262.8	296.9	-	218.4	344.1	261.4	294.5	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K5-525AXSP08	261.4	406.8	311	349.5	-	261	403.4	309.4	346.4	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K5-532AXSP08	244.2	383.4	292	328.7	-	243.8	379.9	290.3	326	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K5-625AXSP08	283	436.5	335.5	375.6	716.2	282.8	431.8	333.3	372.4	705.3	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K5-632AXSP08	267.1	416.8	319	358.1	690.5	266.9	412.5	317.1	355.2	679.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K8-425AXSP08	236.7	372.9	283.4	319.5	-	236.5	369.6	282	317.1	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K8-432AXSP08	218.4	346.8	262.8	296.9	-	218.4	344.1	261.4	294.5	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K8-525AXSP08	261.4	406.8	311	349.5	-	261	403.4	309.4	346.4	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K8-532AXSP08	244.2	383.4	292	328.7	-	243.8	379.9	290.3	326	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K8-625AXSP08	283	436.5	335.5	375.6	716.2	282.8	431.8	333.3	372.4	705.3	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K8-632AXSP08	267.1	416.8	319	358.1	690.5	266.9	412.5	317.1	355.2	679.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K9-425AXSP08	236.7	372.9	283.4	319.5	-	236.5	369.6	282	317.1	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K9-432AXSP08	218.4	346.8	262.8	296.9	-	218.4	344.1	261.4	294.5	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750K9-525AXSP08	261.4	406.8	311	349.5	-	261	403.4	309.4	346.4	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K9-532AXSP08	244.2	383.4	292	328.7	-	243.8	379.9	290.3	326	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750K9-625AXSP08	283	436.5	335.5	375.6	716.2	282.8	431.8	333.3	372.4	705.3	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750K9-632AXSP08	267.1	416.8	319	358.1	690.5	266.9	412.5	317.1	355.2	679.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750R3-425AXSP08	231.8	365.3	277.4	312.6	-	231.5	362	276	310.2	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750R3-432AXSP08	214.3	339.6	257.6	291	-	214.1	337	256.2	288.5	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD1553ZK750R3-525AXSP08	255.6	397.9	304.5	341.5	-	255.2	394	302.4	339	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750R3-532AXSP08	238.7	375.6	285.8	321.6	-	238.6	372	284.1	319	619	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD1553ZK750R3-625AXSP08	276.3	425.9	328	367.1	698.6	276.2	421.4	325.4	363.5	687.9	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1553ZK750R3-632AXSP08	261.2	407.2	311.8	350	674.2	261	403.5	310	347.2	663.8	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD1554PB370C2-425AXSP06	216.6	344.8	261	294.9	-	217.7	342.9	260.6	293.7	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C2-432AXSP06	200.1	320.9	242.2	274.2	-	200.9	319.3	241.5	272.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C2-525AXSP06	243.4	382.6	291.3	328.2	-	244.3	380.5	290.7	326.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB370C2-532AXSP08	238.9	372.6	284.6	319.9	-	238.6	369.4	282.8	317	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB370C2-625AXSP08	272.1	415.6	320.8	358.6	-	271.8	412.1	318.9	355.4	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C2-632AXSP08	259.3	400.5	307.3	344.5	-	259	396.3	305.4	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C4-425AXSP06	216.6	344.8	261	294.9	-	217.7	342.9	260.6	293.7	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C4-432AXSP06	200.1	320.9	242.2	274.2	-	200.9	319.3	241.5	272.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C4-525AXSP06	243.4	382.6	291.3	328.2	-	244.3	380.5	290.7	326.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB370C4-532AXSP08	238.9	372.6	284.6	319.9	-	238.6	369.4	282.8	317	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB370C4-625AXSP08	272.1	415.6	320.8	358.6	-	271.8	412.1	318.9	355.4	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C4-632AXSP08	259.3	400.5	307.3	344.5	-	259	396.3	305.4	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C5-425AXSP06	216.6	344.8	261	294.9	-	217.7	342.9	260.6	293.7	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C5-432AXSP06	200.1	320.9	242.2	274.2	-	200.9	319.3	241.5	272.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C5-525AXSP06	243.4	382.6	291.3	328.2	-	244.3	380.5	290.7	326.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB370C5-532AXSP08	238.9	372.6	284.6	319.9	-	238.6	369.4	282.8	317	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB370C5-625AXSP08	272.1	415.6	320.8	358.6	-	271.8	412.1	318.9	355.4	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C5-632AXSP08	259.3	400.5	307.3	344.5	-	259	396.3	305.4	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C8-425AXSP06	216.6	344.8	261	294.9	-	217.7	342.9	260.6	293.7	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C8-432AXSP06	200.1	320.9	242.2	274.2	-	200.9	319.3	241.5	272.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370C8-525AXSP06	243.4	382.6	291.3	328.2	-	244.3	380.5	290.7	326.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB370C8-532AXSP08	238.9	372.6	284.6	319.9	-	238.6	369.4	282.8	317	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB370C8-625AXSP08	272.1	415.6	320.8	358.6	-	271.8	412.1	318.9	355.4	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370C8-632AXSP08	259.3	400.5	307.3	344.5	-	259	396.3	305.4	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370K2-425AXSP06	208.8	332.1	251.4	284.3	-	209.7	330.1	250.8	282.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370K2-432AXSP06	193.2	309.8	233.5	264.5	-	194	307.6	233	263	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370K2-525AXSP08	244.8	377.8	290.2	324.9	-	244.2	374.4	288	322.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB370K2-532AXSP08	230.1	358.6	274	307.7	-	229.7	355.5	272.5	305.3	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB370K2-625AXSP08	262.1	399.7	308.9	344.7	-	261.4	395.9	306.3	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370K2-632AXSP08	249.9	384.6	295.5	331.1	-	249	381	293.6	328.3	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB370K4-425AXSP06	208.8	332.1	251.4	284.3	-	209.7	330.1	250.8	282.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370K4-432AXSP06	193.2	309.8	233.5	264.5	-	194	307.6	233	263	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB370K4-525AXSP08	244.8	377.8	290.2	324.9	-	244.2	374.4	288	322.2	-	282	27.3	3"	225					

EAW-VD1554PB400K3-532AXSP08	230.1	358.6	274	307.7	-	229.7	355.5	272.5	305.3	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB400K3-625AXSP08	262.1	399.7	308.9	344.7	-	261.4	395.9	306.3	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB400K3-632AXSP08	249.9	384.6	295.5	331.1	-	249	381	293.6	328.3	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB400K9-425AXSP06	208.8	332.1	251.4	284.3	-	209.7	330.1	250.8	282.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB400K9-432AXSP06	193.2	309.8	233.5	264.5	-	194	307.6	233	263	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB400K9-525AXSP08	244.8	377.8	290.2	324.9	-	244.2	374.4	288	322.2	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB400K9-532AXSP08	230.1	358.6	274	307.7	-	229.7	355.5	272.5	305.3	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB400K9-625AXSP08	262.1	399.7	308.9	344.7	-	261.4	395.9	306.3	341.7	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB400K9-632AXSP08	249.9	384.6	295.5	331.1	-	249	381	293.6	328.3	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB400R3-425AXSP06	212.1	337.8	255.5	288.6	-	213.2	336	255.2	287.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB400R3-432AXSP06	196.4	314.8	237.6	268.7	-	197.4	313.4	237.2	267.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB400R3-525AXSP08	248.7	384.1	294.8	330.6	-	248.1	380.7	292.7	327.6	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB400R3-532AXSP08	233.8	364.2	278.5	312.9	-	233.6	361.2	276.7	310.6	-	282	27.3	3"	225	22	2"	338	38.3	3"
EAW-VD1554PB400R3-625AXSP08	266	405.9	313.5	350.4	-	265.4	402.2	311.5	347.5	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB400R3-632AXSP08	253.8	390.9	300.6	336.4	-	253	387.3	298.3	333.6	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550R3-425AXSP06	229.4	366.1	276.8	313.2	-	230.6	364.7	276.4	311.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550R3-432AXSP06	212.3	340.8	256.8	291.1	-	213.4	339.2	256.7	290.2	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550R3-525AXSP06	257.3	405	308.2	347	-	258.4	403.1	307.8	346.2	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550R3-532AXSP06	241.5	383.7	291	328.4	-	242.8	381.9	290.8	327.2	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550R3-625AXSP08	286.9	438.9	338.3	378.4	-	286.8	435.7	336.3	375.9	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550R3-632AXSP08	274	423.6	324.9	364.5	-	273.9	420	323.2	361.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550C2-425AXSP06	241.3	385.2	291.1	329.6	-	242.1	383.6	290.5	328.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C2-432AXSP06	221.9	357.2	269	304.6	-	223	355.3	268.5	303.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C2-525AXSP06	272.6	429.9	326.9	368.3	-	273.6	427.4	326.2	366.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C2-532AXSP06	254.5	405.1	306.5	346.2	-	255.9	403	306.2	344.8	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C2-625AXSP06	294.7	459.5	351.7	394.6	-	295.7	457.2	350.6	393.1	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB550C2-632AXSP08	290.1	449.6	344.7	386.4	-	289.8	446.2	342.6	383.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550C3-425AXSP06	241.3	385.2	291.1	329.6	-	242.1	383.6	290.5	328.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C3-432AXSP06	221.9	357.2	269	304.6	-	223	355.3	268.5	303.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C3-525AXSP06	272.6	429.9	326.9	368.3	-	273.6	427.4	326.2	366.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C3-532AXSP06	254.5	405.1	306.5	346.2	-	255.9	403	306.2	344.8	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C3-625AXSP06	294.7	459.5	351.7	394.6	-	295.7	457.2	350.6	393.1	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB550C3-632AXSP08	290.1	449.6	344.7	386.4	-	289.8	446.2	342.6	383.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550C4-425AXSP06	241.3	385.2	291.1	329.6	-	242.1	383.6	290.5	328.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C4-432AXSP06	221.9	357.2	269	304.6	-	223	355.3	268.5	303.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C4-525AXSP06	272.6	429.9	326.9	368.3	-	273.6	427.4	326.2	366.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C4-532AXSP06	254.5	405.1	306.5	346.2	-	255.9	403	306.2	344.8	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C4-625AXSP06	294.7	459.5	351.7	394.6	-	295.7	457.2	350.6	393.1	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB550C4-632AXSP08	290.1	449.6	344.7	386.4	-	289.8	446.2	342.6	383.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550C5-425AXSP06	241.3	385.2	291.1	329.6	-	242.1	383.6	290.5	328.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C5-432AXSP06	221.9	357.2	269	304.6	-	223	355.3	268.5	303.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C5-525AXSP06	272.6	429.9	326.9	368.3	-	273.6	427.4	326.2	366.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C5-532AXSP06	254.5	405.1	306.5	346.2	-	255.9	403	306.2	344.8	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C5-625AXSP06	294.7	459.5	351.7	394.6	-	295.7	457.2	350.6	393.1	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB550C5-632AXSP08	290.1	449.6	344.7	386.4	-	289.8	446.2	342.6	383.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550C8-425AXSP06	241.3	385.2	291.1	329.6	-	242.1	383.6	290.5	328.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C8-432AXSP06	221.9	357.2	269	304.6	-	223	355.3	268.5	303.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C8-525AXSP06	272.6	429.9	326.9	368.3	-	273.6	427.4	326.2	366.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C8-532AXSP06	254.5	405.1	306.5	346.2	-	255.9	403	306.2	344.8	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C8-625AXSP06	294.7	459.5	351.7	394.6	-	295.7	457.2	350.6	393.1	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB550C8-632AXSP08	290.1	449.6	344.7	386.4	-	289.8	446.2	342.6	383.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550C9-425AXSP06	241.3	385.2	291.1	329.6	-	242.1	383.6	290.5	328.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C9-432AXSP06	221.9	357.2	269	304.6	-	223	355.3	268.5	303.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550C9-525AXSP06	272.6	429.9	326.9	368.3	-	273.6	427.4	326.2	366.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C9-532AXSP06	254.5	405.1	306.5	346.2	-	255.9	403	306.2	344.8	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550C9-625AXSP06	294.7	459.5	351.7	394.6	-	295.7	457.2	350.6	393.1	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB550C9-632AXSP08	290.1	449.6	344.7	386.4	-	289.8	446.2	342.6	383.8	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550K2-425AXSP06	230.9	368.5	278.1	314.6	-	232	366.3	278.1	313.7	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550K2-432AXSP06	213.1	342.2	257.8	292.2	-	214.1	340.4	257.6	291.2	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550K2-525AXSP06	259.7	409	311.1	350.3	-	260.5	406.6	310.4	348.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550K2-532AXSP06	243.1	386.5	292.5	330.7	-	244.4	384.5	292.2	329.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB550K2-625AXSP08	290.8	445.8	343.5	384.2	-	290.5	441.5	341.1	380.9	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550K2-632AXSP08	276.7	427.3	328.1	367.6	-	276.3	423.8	326	365	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD1554PB550K3-425AXSP06	230.9	368.5	278.1	314.6	-	232	366.3	278.1	313.7	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550K3-432AXSP06	213.1	342.2	257.8	292.2	-	214.1	340.4	257.6	291.2	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB550K3-525AXSP06	259.7																		

EAW-VD1554PB750C2-525AXSP06	287.1	454.2	345.2	388.7	-	288.8	452.6	344.6	387.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C2-532AXSP06	268.7	428.7	324	366.4	-	270.2	426.5	323.7	365	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C2-625AXSP06	310	484.4	370.3	415.6	-	311.9	482.6	370	414.5	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C2-632AXSP06	294.3	464.4	352.8	397.5	-	295.8	462.4	352.6	396.3	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C3-425AXSP06	254.8	408.3	308.1	348.7	-	256.4	406.6	308.2	347.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C3-432AXSP06	235	378.3	284.8	322.9	-	236.2	377	284.6	322	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C3-525AXSP06	287.1	454.2	345.2	388.7	-	288.8	452.6	344.6	387.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C3-625AXSP06	310	484.4	370.3	415.6	-	311.9	482.6	370	414.5	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C3-632AXSP06	294.3	464.4	352.8	397.5	-	295.8	462.4	352.6	396.3	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C4-425AXSP06	254.8	408.3	308.1	348.7	-	256.4	406.6	308.2	347.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C4-432AXSP06	235	378.3	284.8	322.9	-	236.2	377	284.6	322	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C4-525AXSP06	287.1	454.2	345.2	388.7	-	288.8	452.6	344.6	387.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C4-532AXSP06	268.7	428.7	324	366.4	-	270.2	426.5	323.7	365	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C4-625AXSP06	310	484.4	370.3	415.6	-	311.9	482.6	370	414.5	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C4-632AXSP06	294.3	464.4	352.8	397.5	-	295.8	462.4	352.6	396.3	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C8-425AXSP06	254.8	408.3	308.1	348.7	-	256.4	406.6	308.2	347.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C8-432AXSP06	235	378.3	284.8	322.9	-	236.2	377	284.6	322	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C8-525AXSP06	287.1	454.2	345.2	388.7	-	288.8	452.6	344.6	387.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C8-532AXSP06	268.7	428.7	324	366.4	-	270.2	426.5	323.7	365	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C8-625AXSP06	310	484.4	370.3	415.6	-	311.9	482.6	370	414.5	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C8-632AXSP06	294.3	464.4	352.8	397.5	-	295.8	462.4	352.6	396.3	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C9-425AXSP06	254.8	408.3	308.1	348.7	-	256.4	406.6	308.2	347.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C9-432AXSP06	235	378.3	284.8	322.9	-	236.2	377	284.6	322	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750C9-525AXSP06	287.1	454.2	345.2	388.7	-	288.8	452.6	344.6	387.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C9-532AXSP06	268.7	428.7	324	366.4	-	270.2	426.5	323.7	365	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750C9-625AXSP06	310	484.4	370.3	415.6	-	311.9	482.6	370	414.5	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750C9-632AXSP06	294.3	464.4	352.8	397.5	-	295.8	462.4	352.6	396.3	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K2-425AXSP06	246.8	394.7	297.8	337.5	-	248.2	393.6	297.8	336.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K2-432AXSP06	227.9	366.9	276.1	312.9	-	229.3	365.7	276	312.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K2-525AXSP06	277.8	438.6	333.3	375.6	-	279.2	436.7	333	374.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K2-532AXSP06	259.8	414.3	313.1	353.8	-	261.7	412.1	313.2	353	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K2-625AXSP06	299.8	467.7	357.9	401.6	-	301.4	465.7	357.4	400.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K2-632AXSP06	284	448.1	341.4	384.4	751	285.7	446.5	340.9	382.9	743	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K3-425AXSP06	246.8	394.7	297.8	337.5	-	248.2	393.6	297.8	336.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K3-432AXSP06	227.9	366.9	276.1	312.9	-	229.3	365.7	276	312.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K3-525AXSP06	277.8	438.6	333.3	375.6	-	279.2	436.7	333	374.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K3-532AXSP06	259.8	414.3	313.1	353.8	-	261.7	412.1	313.2	353	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K3-625AXSP06	299.8	467.7	357.9	401.6	-	301.4	465.7	357.4	400.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K3-632AXSP06	284	448.1	341.4	384.4	751	285.7	446.5	340.9	382.9	743	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K4-425AXSP06	246.8	394.7	297.8	337.5	-	248.2	393.6	297.8	336.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K4-432AXSP06	227.9	366.9	276.1	312.9	-	229.3	365.7	276	312.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K4-525AXSP06	277.8	438.6	333.3	375.6	-	279.2	436.7	333	374.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K4-532AXSP06	259.8	414.3	313.1	353.8	-	261.7	412.1	313.2	353	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K4-625AXSP06	299.8	467.7	357.9	401.6	-	301.4	465.7	357.4	400.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K4-632AXSP06	284	448.1	341.4	384.4	751	285.7	446.5	340.9	382.9	743	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K5-425AXSP06	246.8	394.7	297.8	337.5	-	248.2	393.6	297.8	336.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K5-432AXSP06	227.9	366.9	276.1	312.9	-	229.3	365.7	276	312.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K5-525AXSP06	277.8	438.6	333.3	375.6	-	279.2	436.7	333	374.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K5-532AXSP06	259.8	414.3	313.1	353.8	-	261.7	412.1	313.2	353	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K5-625AXSP06	299.8	467.7	357.9	401.6	-	301.4	465.7	357.4	400.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K5-632AXSP06	284	448.1	341.4	384.4	751	285.7	446.5	340.9	382.9	743	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K8-425AXSP06	246.8	394.7	297.8	337.5	-	248.2	393.6	297.8	336.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K8-432AXSP06	227.9	366.9	276.1	312.9	-	229.3	365.7	276	312.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K8-525AXSP06	277.8	438.6	333.3	375.6	-	279.2	436.7	333	374.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K8-532AXSP06	259.8	414.3	313.1	353.8	-	261.7	412.1	313.2	353	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K8-625AXSP06	299.8	467.7	357.9	401.6	-	301.4	465.7	357.4	400.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K8-632AXSP06	284	448.1	341.4	384.4	751	285.7	446.5	340.9	382.9	743	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K9-425AXSP06	246.8	394.7	297.8	337.5	-	248.2	393.6	297.8	336.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K9-432AXSP06	227.9	366.9	276.1	312.9	-	229.3	365.7	276	312.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750K9-525AXSP06	277.8	438.6	333.3	375.6	-	279.2	436.7	333	374.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K9-532AXSP06	259.8	414.3	313.1	353.8	-	261.7	412.1	313.2	353	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD1554PB750K9-625AXSP06	299.8	467.7	357.9	401.6	-	301.4	465.7	357.4	400.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750K9-632AXSP06	284	448.1	341.4	384.4	751	285.7	446.5	340.9	382.9	743	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD1554PB750R3-425AXSP06	241.6	386.5	292	330.1	-	243.3	384.7	291.9	329	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750R3-432AXSP06	223.5	359.1	270.6	306.5	-	224.8	357.9	270.4	305.9	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD1554PB750R3-525AXSP06	271.6	428.9	326.2	367.5	-	273.3	426.9	325.8	366.2	-	372	21.9	3"	298	14.5	3"	446		

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1554PI370K2-432AXSP06	230	361	274.9	309.4	-	229	357.2	272.6	306.5	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI370K2-525AXSP06	279	428.4	329.8	369.2	-	277.6	423.6	326.6	364.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI370K2-532AXSP06	262	405.7	310.9	349.1	-	261	401.4	308.1	345.2	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI370K2-625AXSP06	301.2	456.8	353.6	394.7	741.8	299.7	450.9	350.4	389.9	729.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI370K2-632AXSP06	286	438.5	338.2	377.9	718.9	284.8	433.4	334.8	373.8	707.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI370K4-425AXSP06	248.6	387.1	295.6	332.1	-	247.6	382.7	293.2	328.6	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI370K4-432AXSP06	230	361	274.9	309.4	-	229	357.2	272.6	306.5	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI370K4-525AXSP06	279	428.4	329.8	369.2	-	277.6	423.6	326.6	364.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI370K4-532AXSP06	262	405.7	310.9	349.1	-	261	401.4	308.1	345.2	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI370K4-625AXSP06	301.2	456.8	353.6	394.7	741.8	299.7	450.9	350.4	389.9	729.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI370K4-632AXSP06	286	438.5	338.2	377.9	718.9	284.8	433.4	334.8	373.8	707.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI370K5-425AXSP06	248.6	387.1	295.6	332.1	-	247.6	382.7	293.2	328.6	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI370K5-432AXSP06	230	361	274.9	309.4	-	229	357.2	272.6	306.5	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI370K5-525AXSP06	279	428.4	329.8	369.2	-	277.6	423.6	326.6	364.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI370K5-532AXSP06	262	405.7	310.9	349.1	-	261	401.4	308.1	345.2	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI370K5-625AXSP06	301.2	456.8	353.6	394.7	741.8	299.7	450.9	350.4	389.9	729.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI370K5-632AXSP06	286	438.5	338.2	377.9	718.9	284.8	433.4	334.8	373.8	707.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400B3-425AXSP06	251.5	391.9	299.6	336.6	-	250.5	388.1	297.3	333.2	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400B3-432AXSP06	233.1	365.5	278.7	313.7	-	232.1	361.7	276.3	310.3	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400B3-525AXSP06	282.7	434.2	334.1	374.1	-	281.4	429.5	331.1	370	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400B3-532AXSP06	265.5	411.4	315.1	353.9	-	264.1	407.1	312.4	350	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400B3-625AXSP06	304.7	462.3	357.8	398.9	750.9	303	456.7	354.4	394.4	738.6	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400B3-632AXSP06	290.1	444.4	342.7	383.4	729.7	288.6	439.4	339.4	379	717.2	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400C3-425AXSP06	257.7	402	307	345.1	-	257	397.9	304.5	341.4	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400C3-432AXSP06	239.9	374.1	284.5	320.4	-	237.3	370.1	282.5	317.3	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400C3-525AXSP06	290.5	446.7	343.5	384.8	-	289.1	441.2	340.2	380.3	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400C3-532AXSP06	272.2	422.3	323.2	363.1	-	270.7	417.1	320.2	358.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400C3-625AXSP06	314.1	477	369.4	411.9	-	312.2	470.9	365.6	406.9	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400C3-632AXSP06	298.1	457.1	352.3	393.7	751	296.5	451.8	348.7	389.5	737.9	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400C9-425AXSP06	257.7	402	307	345.1	-	257	397.9	304.5	341.4	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400C9-432AXSP06	237.9	374.1	284.5	320.4	-	237.3	370.1	282.5	317.3	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400C9-525AXSP06	290.5	446.7	343.5	384.8	-	289.1	441.2	340.2	380.3	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400C9-532AXSP06	272.2	422.3	323.2	363.1	-	270.7	417.1	320.2	358.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400C9-625AXSP06	314.1	477	369.4	411.9	-	312.2	470.9	365.6	406.9	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400C9-632AXSP06	298.1	457.1	352.3	393.7	751	296.5	451.8	348.7	389.5	737.9	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400K3-425AXSP06	248.6	387.1	295.6	332.1	-	247.6	382.7	293.2	328.6	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400K3-432AXSP06	230	361	274.9	309.4	-	229	357.2	272.6	306.5	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400K3-525AXSP06	279	428.4	329.8	369.2	-	277.6	423.6	326.6	364.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400K3-532AXSP06	262	405.7	310.9	349.1	-	261	401.4	308.1	345.2	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400K3-625AXSP06	301.2	456.8	353.6	394.7	741.8	299.7	450.9	350.4	389.9	729.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400K3-632AXSP06	286	438.5	338.2	377.9	718.9	284.8	433.4	334.8	373.8	707.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400K9-425AXSP06	248.6	387.1	295.6	332.1	-	247.6	382.7	293.2	328.6	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400K9-432AXSP06	230	361	274.9	309.4	-	229	357.2	272.6	306.5	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400K9-525AXSP06	279	428.4	329.8	369.2	-	277.6	423.6	326.6	364.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400K9-532AXSP06	262	405.7	310.9	349.1	-	261	401.4	308.1	345.2	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400K9-625AXSP06	301.2	456.8	353.6	394.7	741.8	299.7	450.9	350.4	389.9	729.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400K9-632AXSP06	286	438.5	338.2	377.9	718.9	284.8	433.4	334.8	373.8	707.1	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400R3-425AXSP06	253.4	395	301.9	339.3	-	252.5	390.7	299.1	335.9	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400R3-432AXSP06	234.5	368.5	280.4	315.7	-	233.6	364.7	278.1	312.8	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI400R3-525AXSP06	284.3	437.5	336.6	376.4	-	283	432.2	333.5	372.7	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400R3-532AXSP06	267.1	414.6	317.5	356.1	-	266.2	409.7	314.8	352.3	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI400R3-625AXSP06	307.1	466	360.6	402.6	-	305.3	460.2	357.1	397.9	744.4	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI400R3-632AXSP06	291.8	447.7	344.7	385.8	734.4	290.3	442.1	341.9	381.3	721.7	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI550B3-425AXSP04	262.7	422.9	319	361.3	716.1	264.2	420.1	318.8	359.4	706.7	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554PI550B3-432AXSP06	254.8	401.9	305.2	344.1	-	254.1	397.4	302.9	340.7	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD1554PI550B3-525AXSP06	310.9	479.4	368.4	412.9	-	309.9	474.7	365.4	408.8	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI550B3-532AXSP06	291.5	453.2	347	389.6	-	290.5	449	343.9	385.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI550B3-625AXSP06	336	511.3	395.3	441.7	-	334.7	505.7	392.1	437.2	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI550B3-632AXSP06	319.4	491	377.6	422.9	-	317.7	485.4	374.4	418.5	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI550C2-425AXSP04	274.7	442.1	334	377.8	751.2	276.8	439.7	333	375.7	740.9	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554PI550C2-432AXSP04	251.8	410.1	308.3	349.6	700.8	253.8	407.8	307.9	348.1	691.7	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554PI550C2-525AXSP04	307.2	490.2	372.1	419.9	823	309.1	486.9	371.5	417.5	811.5	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD1554PI550C2-532AXSP06	305.1	475.4	362.8	407.7	-	303.8	470	359.9	404.1	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554PI550C2-625AXSP06	355	541.8	418.4	467.7	-	353.2	535.3	414.4	462.4	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PI550C2-632AXSP06	335.2	517.1	397.1	445															

EAW-VD15S4PI50K2-425AXSP04	263	423.6	320.1	361.8	718.4	265.1	420.8	319.3	360.5	709	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI50K2-432AXSP06	255.7	402.6	306.2	344.7	-	255	398.9	304	341.9	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD15S4PI50K2-525AXSP06	311.9	481.8	369.7	414.4	-	310.8	476.3	366.6	410.1	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50K2-532AXSP06	292.1	454.8	347.7	390.4	-	290.9	449.8	345	386.5	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50K2-625AXSP06	337.6	514.5	397.8	443.8	-	336.5	508.5	394.2	439.6	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50K2-632AXSP06	320.5	492.8	378.9	424.4	-	319.1	487	375.6	419.8	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50K3-425AXSP04	263	423.6	320.1	361.8	718.4	265.1	420.8	319.3	360.5	709	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI50K3-432AXSP06	255.7	402.6	306.2	344.7	-	255	398.9	304	341.9	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD15S4PI50K3-525AXSP06	311.9	481.8	369.7	414.4	-	310.8	476.3	366.6	410.1	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50K3-532AXSP06	292.1	454.8	347.7	390.4	-	290.9	449.8	345	386.5	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50K3-625AXSP06	337.6	514.5	397.8	443.8	-	336.5	508.5	394.2	439.6	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50K3-632AXSP06	320.5	492.8	378.9	424.4	-	319.1	487	375.6	419.8	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50K9-425AXSP04	263	423.6	320.1	361.8	718.4	265.1	420.8	319.3	360.5	709	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI50K9-432AXSP06	255.7	402.6	306.2	344.7	-	255	398.9	304	341.9	-	293	26.9	3"	234	22.1	2"	352	37.7	3"
EAW-VD15S4PI50K9-525AXSP06	311.9	481.8	369.7	414.4	-	310.8	476.3	366.6	410.1	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50K9-532AXSP06	292.1	454.8	347.7	390.4	-	290.9	449.8	345	386.5	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50K9-625AXSP06	337.6	514.5	397.8	443.8	-	336.5	508.5	394.2	439.6	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50K9-632AXSP06	320.5	492.8	378.9	424.4	-	319.1	487	375.6	419.8	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50R3-425AXSP04	270.6	435.1	328.3	372	738.8	272.4	433.1	328.3	370.3	729.4	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI50R3-432AXSP04	248.7	404.8	304.3	345.1	691.3	250.6	402.8	304.3	344	682.8	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI50R3-525AXSP06	320.7	495.1	380.1	425.6	-	319.2	489.6	377.1	421.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50R3-532AXSP06	300.1	467.2	356.8	401.5	-	299.1	462.3	354.3	397	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI50R3-625AXSP06	346.8	528.9	408.7	456.7	-	345.4	523.2	405.3	452.1	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI50R3-632AXSP06	328.9	506.3	389.6	435.8	-	327.7	501.2	386.3	431.9	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C2-425AXSP04	295.1	473.8	357.3	404.8	-	296.9	472.1	357	403.3	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C2-432AXSP04	270.3	439.7	330.3	374.7	-	272.4	437.1	329.9	373	744.1	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C2-525AXSP04	329.4	525	398.7	449.6	883.5	331.5	522.3	398.2	447.9	872.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C2-532AXSP04	306	493.7	373.1	422.4	837.1	308.6	491.4	373	420.4	826.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C2-625AXSP06	378.7	580.2	447.3	500.3	-	377.6	574.3	443.9	495.5	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C2-632AXSP06	358.4	553.8	424.9	476.6	-	357.6	548.1	421.8	472.1	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C3-425AXSP04	295.1	473.8	357.3	404.8	-	296.9	472.1	357	403.3	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C3-432AXSP04	270.3	439.7	330.3	374.7	-	272.4	437.1	329.9	373	744.1	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C3-525AXSP04	329.4	525	398.7	449.6	883.5	331.5	522.3	398.2	447.9	872.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C3-532AXSP04	306	493.7	373.1	422.4	837.1	308.6	491.4	373	420.4	826.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C3-625AXSP06	378.7	580.2	447.3	500.3	-	377.6	574.3	443.9	495.5	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C3-632AXSP06	358.4	553.8	424.9	476.6	-	357.6	548.1	421.8	472.1	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C4-425AXSP04	295.1	473.8	357.3	404.8	-	296.9	472.1	357	403.3	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C4-432AXSP04	270.3	439.7	330.3	374.7	-	272.4	437.1	329.9	373	744.1	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C4-525AXSP04	329.4	525	398.7	449.6	883.5	331.5	522.3	398.2	447.9	872.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C4-532AXSP04	306	493.7	373.1	422.4	837.1	308.6	491.4	373	420.4	826.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C4-625AXSP06	378.7	580.2	447.3	500.3	-	377.6	574.3	443.9	495.5	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C4-632AXSP06	358.4	553.8	424.9	476.6	-	357.6	548.1	421.8	472.1	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C5-425AXSP04	295.1	473.8	357.3	404.8	-	296.9	472.1	357	403.3	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C5-432AXSP04	270.3	439.7	330.3	374.7	-	272.4	437.1	329.9	373	744.1	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C5-525AXSP04	329.4	525	398.7	449.6	883.5	331.5	522.3	398.2	447.9	872.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C5-532AXSP04	306	493.7	373.1	422.4	837.1	308.6	491.4	373	420.4	826.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C5-625AXSP06	378.7	580.2	447.3	500.3	-	377.6	574.3	443.9	495.5	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C5-632AXSP06	358.4	553.8	424.9	476.6	-	357.6	548.1	421.8	472.1	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C8-425AXSP04	295.1	473.8	357.3	404.8	-	296.9	472.1	357	403.3	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C8-432AXSP04	270.3	439.7	330.3	374.7	-	272.4	437.1	329.9	373	744.1	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C8-525AXSP04	329.4	525	398.7	449.6	883.5	331.5	522.3	398.2	447.9	872.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C8-532AXSP04	306	493.7	373.1	422.4	837.1	308.6	491.4	373	420.4	826.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C9-425AXSP04	295.1	473.8	357.3	404.8	-	296.9	472.1	357	403.3	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C9-432AXSP04	270.3	439.7	330.3	374.7	-	272.4	437.1	329.9	373	744.1	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750C9-525AXSP04	329.4	525	398.7	449.6	883.5	331.5	522.3	398.2	447.9	872.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C9-532AXSP04	306	493.7	373.1	422.4	837.1	308.6	491.4	373	420.4	826.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750C9-625AXSP06	378.7	580.2	447.3	500.3	-	377.6	574.3	443.9	495.5	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750C9-632AXSP06	358.4	553.8	424.9	476.6	-	357.6	548.1	421.8	472.1	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750K2-425AXSP04	261.9	425.8	320.1	363.2	728	263.9	423.4	319.6	361.7	719.6	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750K2-432AXSP04	219.5	506.7	384.7	433.7	851.7	319.9	503.9	384.1	431.9	840.8	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD15S4PI750K2-532AXSP06	315.4	492.4	375.9	422.6	-	314.7	487.6	372.9	418.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD15S4PI750K2-625AXSP06	365	558.5	430.4	481.2	-	364	552.2	427.2	476.7	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750K2-632AXSP06	346.5	534.4	410	459.6	-	345	528.7	406.8	455.2	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD15S4PI750K3-425AXSP04	285.1	458.4	345.7	391.4	-	286.8	455.9	345.3	389.8	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD15S4PI750K3-432AXSP04	261.9	425.8	320.1	363.2	728	263.9	423.4	319.6	361.7	719.6	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW																			

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1554P1750K5-632AXSP06	346.5	534.4	410	459.6	-	345	528.7	406.8	455.2	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554P1750K8-425AXSP04	285.1	458.4	345.7	391.4	-	286.8	455.9	345.3	389.8	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554P1750K8-432AXSP04	261.9	425.8	320.1	363.2	728	263.9	423.4	319.6	361.7	719.6	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554P1750K8-525AXSP04	317.5	506.7	384.7	433.7	851.7	319.9	503.9	384.1	431.9	840.8	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD1554P1750K8-532AXSP06	315.4	492.4	375.9	422.6	-	314.7	487.6	372.9	418.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554P1750K8-625AXSP06	365	558.5	430.4	481.2	-	364	552.2	427.2	476.7	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554P1750K8-632AXSP06	346.5	534.4	410	459.6	-	345	528.7	406.8	455.2	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554P1750K9-425AXSP04	285.1	458.4	345.7	391.4	-	286.8	455.9	345.3	389.8	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554P1750K9-432AXSP04	261.9	425.8	320.1	363.2	728	263.9	423.4	319.6	361.7	719.6	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554P1750K9-525AXSP04	317.5	506.7	384.7	433.7	851.7	319.9	503.9	384.1	431.9	840.8	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD1554P1750K9-532AXSP06	315.4	492.4	375.9	422.6	-	314.7	487.6	372.9	418.9	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554P1750K9-625AXSP06	365	558.5	430.4	481.2	-	364	552.2	427.2	476.7	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554P1750K9-632AXSP06	346.5	534.4	410	459.6	-	345	528.7	406.8	455.2	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554P1750R3-425AXSP04	278.7	449.1	338.4	383	-	280.9	446.6	338	381.5	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554P1750R3-432AXSP04	256.4	417.1	313.5	356	713.5	258.6	415.4	313.3	354.4	705.2	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD1554P1750R3-525AXSP04	309.9	495.6	376	424.4	831.2	312.2	492.1	375.3	422.5	820.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD1554P1750R3-532AXSP06	308.7	481.4	367.8	413.3	-	307.9	476.7	365.5	409.7	-	372	27.9	3"	298	18.4	3"	446	39.1	3"
EAW-VD1554P1750R3-625AXSP06	356.7	544.6	420.5	469.4	-	355.6	539.1	417.3	465	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554P1750R3-632AXSP06	338.6	521.9	401.2	449.7	-	337.6	516.3	398.1	445.3	-	451	29.1	3"	361	19.2	3"	541	37.2	4"
EAW-VD1554PK370C2-425AXSP06	232.1	366.2	278.2	313.9	-	232.2	363.5	276.7	311.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C2-432AXSP06	214.3	340.9	257.6	291.4	-	214.5	338.2	256.6	289.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C2-525AXSP06	261	406.7	310.9	349.4	-	261	403.3	309.4	346.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C2-532AXSP06	244.5	384.6	292.9	329.7	-	244.8	381.4	291.5	327.3	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C2-625AXSP06	281.4	433.9	333.6	373.4	711.9	281.3	430	331.5	370.4	701.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK370C2-632AXSP08	276.9	424.5	326.9	365.6	-	275.7	420	324	362.1	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370C4-425AXSP06	232.1	366.2	278.2	313.9	-	232.2	363.5	276.7	311.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C4-432AXSP06	214.3	340.9	257.6	291.4	-	214.5	338.2	256.6	289.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C4-525AXSP06	261	406.7	310.9	349.4	-	261	403.3	309.4	346.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C4-532AXSP06	244.5	384.6	292.9	329.7	-	244.8	381.4	291.5	327.3	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C4-625AXSP06	281.4	433.9	333.6	373.4	711.9	281.3	430	331.5	370.4	701.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK370C4-632AXSP08	276.9	424.5	326.9	365.6	-	275.7	420	324	362.1	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370C5-425AXSP06	232.1	366.2	278.2	313.9	-	232.2	363.5	276.7	311.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C5-432AXSP06	214.3	340.9	257.6	291.4	-	214.5	338.2	256.6	289.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C5-525AXSP06	261	406.7	310.9	349.4	-	261	403.3	309.4	346.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C5-532AXSP06	244.5	384.6	292.9	329.7	-	244.8	381.4	291.5	327.3	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C5-625AXSP06	281.4	433.9	333.6	373.4	711.9	281.3	430	331.5	370.4	701.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK370C5-632AXSP08	276.9	424.5	326.9	365.6	-	275.7	420	324	362.1	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370C8-425AXSP06	232.1	366.2	278.2	313.9	-	232.2	363.5	276.7	311.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C8-432AXSP06	214.3	340.9	257.6	291.4	-	214.5	338.2	256.6	289.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370C8-525AXSP06	261	406.7	310.9	349.4	-	261	403.3	309.4	346.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C8-532AXSP06	244.5	384.6	292.9	329.7	-	244.8	381.4	291.5	327.3	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370C8-625AXSP06	281.4	433.9	333.6	373.4	711.9	281.3	430	331.5	370.4	701.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK370C8-632AXSP08	276.9	424.5	326.9	365.6	-	275.7	420	324	362.1	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K2-425AXSP06	223.5	352.5	267.7	301.9	-	223.6	349.8	266.7	300	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K2-432AXSP06	206.8	328.4	248.6	281	-	206.8	325.7	247.6	279	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K2-525AXSP06	251.2	390.7	298.7	335.5	-	251.1	387.4	297.1	332.9	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K2-532AXSP06	235.4	370.1	281.8	317	619	235.6	366.9	280.4	314.7	610.2	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K2-625AXSP08	279.7	423.8	328.1	365.9	-	278.2	418.8	324.9	361.8	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K2-632AXSP08	266.5	407.9	314	351.6	-	265.2	403	311.6	347.6	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K4-425AXSP06	223.5	352.5	267.7	301.9	-	223.6	349.8	266.7	300	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K4-432AXSP06	206.8	328.4	248.6	281	-	206.8	325.7	247.6	279	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K4-525AXSP06	251.2	390.7	298.7	335.5	-	251.1	387.4	297.1	332.9	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K4-532AXSP06	235.4	370.1	281.8	317	619	235.6	366.9	280.4	314.7	610.2	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K4-625AXSP08	279.7	423.8	328.1	365.9	-	278.2	418.8	324.9	361.8	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K4-632AXSP08	266.5	407.9	314	351.6	-	265.2	403	311.6	347.6	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K5-425AXSP06	223.5	352.5	267.7	301.9	-	223.6	349.8	266.7	300	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K5-432AXSP06	206.8	328.4	248.6	281	-	206.8	325.7	247.6	279	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K5-525AXSP06	251.2	390.7	298.7	335.5	-	251.1	387.4	297.1	332.9	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K5-532AXSP06	235.4	370.1	281.8	317	619	235.6	366.9	280.4	314.7	610.2	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K5-625AXSP08	279.7	423.8	328.1	365.9	-	278.2	418.8	324.9	361.8	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K5-632AXSP08	266.5	407.9	314	351.6	-	265.2	403	311.6	347.6	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK370K8-425AXSP06	223.5	352.5	267.7	301.9	-	223.6	349.8	266.7	300	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K8-432AXSP06	206.8	328.4	248.6	281	-	206.8	325.7	247.6	279	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK370K8-525AXSP06	251.2	390.7	298.7	335.5	-	251.1	387.4	297.1	332.9	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK370K8-532AXSP06	235.4	370.1	281.8	317	619	235.6	366.9	280.4	314.7										

EAW-VD1554PK400R3-625AXSP08	284.3	431.1	334	372	-	282.9	426.1	330.9	368.5	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK400R3-632AXSP08	271.1	415.2	319.5	357.8	-	269.9	410.4	317.1	353.9	-	338	30.6	3"	270	20.2	3"	406	42.9	3"
EAW-VD1554PK550B3-425AXSP06	246.7	391	296.6	334.5	-	247.4	388	295.5	332.4	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550B3-432AXSP06	228	363.5	274.7	310.7	-	228.4	361.1	273.6	309.1	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550B3-525AXSP06	277	433.1	330.9	371.6	-	277.6	430.1	329.3	369.5	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550B3-532AXSP06	260.1	410	311.9	351.5	-	260.6	406.8	310.6	349.1	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550B3-625AXSP06	298.7	460.3	353.8	396.3	-	298.9	457.2	352.4	394	748.4	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550B3-632AXSP06	284.1	443.2	339	380.9	735.5	284.4	440	337.6	377.9	726.2	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C2-425AXSP06	258.5	410.4	311.2	351.2	-	259.2	407.1	309.9	348.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C2-432AXSP06	238	380	287	324.9	-	238.4	377.4	286	322.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C2-525AXSP06	292.6	458	349.2	393	-	293	454.6	347.8	390.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C2-532AXSP06	273.2	431.2	327.3	369.2	-	273.5	428.1	326.2	367	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C2-625AXSP06	317.1	490.6	376.4	421.9	-	317.5	486.7	374.5	419	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C2-632AXSP06	300.5	468.6	358.2	402.2	-	300.7	464.9	356.6	399.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C3-425AXSP06	258.5	410.4	311.2	351.2	-	259.2	407.1	309.9	348.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C3-432AXSP06	238	380	287	324.9	-	238.4	377.4	286	322.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C3-525AXSP06	292.6	458	349.2	393	-	293	454.6	347.8	390.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C3-532AXSP06	273.2	431.2	327.3	369.2	-	273.5	428.1	326.2	367	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C3-625AXSP06	317.1	490.6	376.4	421.9	-	317.5	486.7	374.5	419	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C3-632AXSP06	300.5	468.6	358.2	402.2	-	300.7	464.9	356.6	399.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C4-425AXSP06	258.5	410.4	311.2	351.2	-	259.2	407.1	309.9	348.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C4-432AXSP06	238	380	287	324.9	-	238.4	377.4	286	322.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C4-525AXSP06	292.6	458	349.2	393	-	293	454.6	347.8	390.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C4-532AXSP06	273.2	431.2	327.3	369.2	-	273.5	428.1	326.2	367	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C4-625AXSP06	317.1	490.6	376.4	421.9	-	317.5	486.7	374.5	419	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C4-632AXSP06	300.5	468.6	358.2	402.2	-	300.7	464.9	356.6	399.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C5-425AXSP06	258.5	410.4	311.2	351.2	-	259.2	407.1	309.9	348.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C5-432AXSP06	238	380	287	324.9	-	238.4	377.4	286	322.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C5-525AXSP06	292.6	458	349.2	393	-	293	454.6	347.8	390.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C5-532AXSP06	273.2	431.2	327.3	369.2	-	273.5	428.1	326.2	367	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C5-625AXSP06	317.1	490.6	376.4	421.9	-	317.5	486.7	374.5	419	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C5-632AXSP06	300.5	468.6	358.2	402.2	-	300.7	464.9	356.6	399.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C8-425AXSP06	258.5	410.4	311.2	351.2	-	259.2	407.1	309.9	348.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C8-432AXSP06	238	380	287	324.9	-	238.4	377.4	286	322.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C8-525AXSP06	292.6	458	349.2	393	-	293	454.6	347.8	390.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C8-532AXSP06	273.2	431.2	327.3	369.2	-	273.5	428.1	326.2	367	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C8-625AXSP06	317.1	490.6	376.4	421.9	-	317.5	486.7	374.5	419	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C8-632AXSP06	300.5	468.6	358.2	402.2	-	300.7	464.9	356.6	399.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C9-425AXSP06	258.5	410.4	311.2	351.2	-	259.2	407.1	309.9	348.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C9-432AXSP06	238	380	287	324.9	-	238.4	377.4	286	322.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550C9-525AXSP06	292.6	458	349.2	393	-	293	454.6	347.8	390.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C9-532AXSP06	273.2	431.2	327.3	369.2	-	273.5	428.1	326.2	367	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550C9-625AXSP06	317.1	490.6	376.4	421.9	-	317.5	486.7	374.5	419	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550C9-632AXSP06	300.5	468.6	358.2	402.2	-	300.7	464.9	356.6	399.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K2-425AXSP06	240.6	392.5	297.8	335.8	-	248.2	389.4	296.6	333.6	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K2-432AXSP06	228.5	364.4	275.6	311.4	-	229.1	361.9	274.7	309.7	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K2-525AXSP06	279	435.6	332.8	374.3	-	279.4	432.5	331.5	372	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K2-532AXSP06	261.4	412.1	313.5	352.7	-	261.6	408.5	311.9	350.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K2-625AXSP06	301.7	465.1	357.3	400.3	-	301.5	461.4	355.5	397.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K2-632AXSP06	285.7	445.8	340.9	383.1	741	286.3	442.4	339.4	380.5	731.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K3-425AXSP06	247.6	392.5	297.8	335.8	-	248.2	389.4	296.6	333.6	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K3-432AXSP06	228.5	364.4	275.6	311.4	-	229.1	361.9	274.7	309.7	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K3-525AXSP06	279	435.6	332.8	374.3	-	279.4	432.5	331.5	372	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K3-532AXSP06	261.4	412.1	313.5	352.7	-	261.6	408.5	311.9	350.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K3-625AXSP06	301.7	465.1	357.3	400.3	-	301.5	461.4	355.5	397.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K3-632AXSP06	285.7	445.8	340.9	383.1	741	286.3	442.4	339.4	380.5	731.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K4-425AXSP06	247.6	392.5	297.8	335.8	-	248.2	389.4	296.6	333.6	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K4-432AXSP06	228.5	364.4	275.6	311.4	-	229.1	361.9	274.7	309.7	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K4-525AXSP06	279	435.6	332.8	374.3	-	279.4	432.5	331.5	372	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K4-532AXSP06	261.4	412.1	313.5	352.7	-	261.6	408.5	311.9	350.6	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K4-625AXSP06	301.7	465.1	357.3	400.3	-	301.5	461.4	355.5	397.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K4-632AXSP06	285.7	445.8	340.9	383.1	741	286.3	442.4	339.4	380.5	731.3	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK550K5-425AXSP06	247.6	392.5	297.8	335.8	-	248.2	389.4	296.6	333.6	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K5-432AXSP06	228.5	364.4	275.6	311.4	-	229.1	361.9	274.7	309.7	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK550K5-525AXSP06	279	435.6	332.8	374.3	-	279.4	432.5	331.5	372	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK550K5-532AXSP06	261.4	412.1	313																

EAW-VD1554PK750C4-532AXSP06	290	458.7	347.9	392.8	-	290.4	455.5	346.8	390.5	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C4-625AXSP06	335.6	519.7	398.6	447.1	-	336.3	516.7	397.5	444.9	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C4-632AXSP06	318.1	497.5	379.6	427.1	-	318.9	494.5	378.5	425	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C5-425AXSP04	257.1	424.2	317.2	361	731.4	261.3	424.1	318.6	361.6	724.5	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750C5-432AXSP06	253	404.3	305.5	345.5	-	253.6	402.2	304.7	343.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750C5-525AXSP06	310	486.8	371	417.3	-	311.1	483.4	369.6	415.4	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C5-532AXSP06	290	458.7	347.9	392.8	-	290.4	455.5	346.8	390.5	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C5-632AXSP06	335.6	519.7	398.6	447.1	-	336.3	516.7	397.5	444.9	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C5-632AXSP06	318.1	497.5	379.6	427.1	-	318.9	494.5	378.5	425	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C8-425AXSP04	257.1	424.2	317.2	361	731.4	261.3	424.1	318.6	361.6	724.5	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750C8-432AXSP06	253	404.3	305.5	345.5	-	253.6	402.2	304.7	343.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750C8-525AXSP06	310	486.8	371	417.3	-	311.1	483.4	369.6	415.4	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C8-532AXSP06	290	458.7	347.9	392.8	-	290.4	455.5	346.8	390.5	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C8-625AXSP06	335.6	519.7	398.6	447.1	-	336.3	516.7	397.5	444.9	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C8-632AXSP06	318.1	497.5	379.6	427.1	-	318.9	494.5	378.5	425	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C9-425AXSP04	257.1	424.2	317.2	361	731.4	261.3	424.1	318.6	361.6	724.5	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750C9-432AXSP06	253	404.3	305.5	345.5	-	253.6	402.2	304.7	343.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750C9-525AXSP06	310	486.8	371	417.3	-	311.1	483.4	369.6	415.4	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C9-532AXSP06	290	458.7	347.9	392.8	-	290.4	455.5	346.8	390.5	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750C9-625AXSP06	335.6	519.7	398.6	447.1	-	336.3	516.7	397.5	444.9	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C9-632AXSP06	318.1	497.5	379.6	427.1	-	318.9	494.5	378.5	425	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750C9-632AXSP06	248.3	410.6	306.9	349.2	706.6	252.6	410.4	308.3	349.6	699.9	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750K2-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K2-525AXSP06	299.5	469.3	358.1	402.6	-	300.4	466.6	356.7	400.7	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K2-532AXSP06	280.4	443.3	336.7	379.3	-	281.3	440.3	335.7	377.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K2-625AXSP06	323.6	501	384.7	431.3	-	324.4	497.7	382.8	428.3	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K2-632AXSP06	307.3	479.8	366.5	412.2	-	308	476.8	365.5	409.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K3-425AXSP04	248.3	410.6	306.9	349.2	706.6	252.6	410.4	308.3	349.6	699.9	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750K3-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K3-525AXSP06	299.5	469.3	358.1	402.6	-	300.4	466.6	356.7	400.7	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K3-532AXSP06	280.4	443.3	336.7	379.3	-	281.3	440.3	335.7	377.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K3-625AXSP06	323.6	501	384.7	431.3	-	324.4	497.7	382.8	428.3	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K3-632AXSP06	307.3	479.8	366.5	412.2	-	308	476.8	365.5	409.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K4-425AXSP04	248.3	410.6	306.9	349.2	706.6	252.6	410.4	308.3	349.6	699.9	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750K4-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K4-525AXSP06	299.5	469.3	358.1	402.6	-	300.4	466.6	356.7	400.7	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K4-532AXSP06	280.4	443.3	336.7	379.3	-	281.3	440.3	335.7	377.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K4-625AXSP06	323.6	501	384.7	431.3	-	324.4	497.7	382.8	428.3	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K4-632AXSP06	307.3	479.8	366.5	412.2	-	308	476.8	365.5	409.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K5-425AXSP04	248.3	410.6	306.9	349.2	706.6	252.6	410.4	308.3	349.6	699.9	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750K5-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K5-525AXSP06	299.5	469.3	358.1	402.6	-	300.4	466.6	356.7	400.7	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K5-532AXSP06	280.4	443.3	336.7	379.3	-	281.3	440.3	335.7	377.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K5-625AXSP06	323.6	501	384.7	431.3	-	324.4	497.7	382.8	428.3	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K5-632AXSP06	307.3	479.8	366.5	412.2	-	308	476.8	365.5	409.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K8-425AXSP04	248.3	410.6	306.9	349.2	706.6	252.6	410.4	308.3	349.6	699.9	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750K8-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K8-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K8-525AXSP06	299.5	469.3	358.1	402.6	-	300.4	466.6	356.7	400.7	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K8-525AXSP06	280.4	443.3	336.7	379.3	-	281.3	440.3	335.7	377.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K8-625AXSP06	323.6	501	384.7	431.3	-	324.4	497.7	382.8	428.3	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K8-625AXSP06	307.3	479.8	366.5	412.2	-	308	476.8	365.5	409.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K8-632AXSP06	248.3	410.6	306.9	349.2	706.6	252.6	410.4	308.3	349.6	699.9	451	18	3"	361	11.8	3"	541	21.7	4"
EAW-VD1554PK750K9-432AXSP06	245.4	391.9	295.8	334.6	-	245.9	389.8	294.9	332.8	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750K9-432AXSP06	299.5	469.3	358.1	402.6	-	300.4	466.6	356.7	400.7	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K9-532AXSP06	280.4	443.3	336.7	379.3	-	281.3	440.3	335.7	377.8	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750K9-625AXSP06	323.6	501	384.7	431.3	-	324.4	497.7	382.8	428.3	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750K9-632AXSP06	307.3	479.8	366.5	412.2	-	308	476.8	365.5	409.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750R3-425AXSP06	260.7	413.2	313.2	353.6	-	261.4	410.8	312.6	351.9	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750R3-432AXSP06	240.4	383.8	290	328.1	-	241.1	381.6	289.4	326.7	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD1554PK750R3-525AXSP06	293.1	458.8	349.9	393.8	-	293.5	455.4	349	391.3	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750R3-532AXSP06	274.8	433.2	329.3	371.4	-	275.1	430.9	328.3	369.3	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD1554PK750R3-625AXSP06	316.4	489.3	375.5	420.9	-	316.7	485.4	374.1	418.4	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554PK750R3-632AXSP06	300.4	469.2	358.1	402.7	-	301	466.1	357	400.5	-	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD1554ZB370C2-432AXSP08	264.1	411	314.5	353.2	-	262.8	406.6	311.2	349.3	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB370C2-432AXSP08	243.9	383	291.4	328.5	-	243.1	378.7	289.											

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1554ZB370K5-525AXSP08	279.5	429.1	330.3	369.8	-	278	424.3	327.1	365.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB370K5-532AXSP08	262.3	406.3	311.3	349.5	-	261.2	401.9	308.4	345.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB370K5-625AXSP08	301.8	457.8	354.4	395.5	743.5	300.3	451.8	351.1	390.7	730.7	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB370K5-632AXSP08	286.4	439.2	338.8	378.5	720.3	285.2	434.1	335.4	374.5	708.4	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB370K8-425AXSP08	254.4	395.7	302.7	339.8	-	253.2	391	299.7	336.2	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB370K8-432AXSP08	235.8	369.6	281.6	316.7	-	235	365.5	279	313.5	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB370K8-525AXSP08	279.5	429.1	330.3	369.8	-	278	424.3	327.1	365.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB370K8-625AXSP08	262.3	406.3	311.3	349.5	-	261.2	401.9	308.4	345.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB370K8-632AXSP08	301.8	457.8	354.4	395.5	743.5	300.3	451.8	351.1	390.7	730.7	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB370K8-632AXSP08	286.4	439.2	338.8	378.5	720.3	285.2	434.1	335.4	374.5	708.4	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400K3-425AXSP08	257.8	400.7	306.4	344.6	-	256.7	396.7	303.9	340.9	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400K3-432AXSP08	239	374.2	285.5	321.1	-	237.9	370.2	282.9	318	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400K3-525AXSP08	283.2	435	334.8	374.9	-	281.8	430.2	331.6	370.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400K3-532AXSP08	265.8	412	315.5	354.4	-	264.4	407	312.7	350.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400K3-625AXSP08	305.5	463.5	358.7	399.9	-	303.7	457.8	355.2	395.3	740.5	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400K3-632AXSP08	290.7	445.3	343.4	384.2	731.3	289.1	440.2	339.9	379.6	718.5	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400C3-425AXSP08	264.1	411	314.5	353.2	-	262.8	406.6	311.2	349.3	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400C3-432AXSP08	243.9	383	291.4	328.5	-	243.1	378.7	289.2	324.6	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400C3-525AXSP08	291	447.4	344	385.4	-	289.5	441.9	340.7	380.9	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400C3-532AXSP08	272.4	422.7	323.5	363.4	-	271.3	417.5	320.5	359.3	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400C3-625AXSP08	314.8	478	370.2	412.8	-	312.8	471.8	366.3	407.7	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400C3-632AXSP08	298.6	457.9	352.8	394.3	752.4	297	452.6	349.3	390.1	739.2	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400C9-425AXSP08	264.1	411	314.5	353.2	-	262.8	406.6	311.2	349.3	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400C9-432AXSP08	243.9	383	291.4	328.5	-	243.1	378.7	289.2	324.6	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400C9-525AXSP08	291	447.4	344	385.4	-	289.5	441.9	340.7	380.9	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400C9-532AXSP08	272.4	422.7	323.5	363.4	-	271.3	417.5	320.5	359.3	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400C9-625AXSP08	314.8	478	370.2	412.8	-	312.8	471.8	366.3	407.7	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400C9-632AXSP08	298.6	457.9	352.8	394.3	752.4	297	452.6	349.3	390.1	739.2	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400K3-425AXSP08	254.4	395.7	302.7	339.8	-	253.2	391	299.7	336.2	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400K3-432AXSP08	235.8	369.6	281.6	316.7	-	235	365.5	279	313.5	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400K3-525AXSP08	279.5	429.1	330.3	369.8	-	278	424.3	327.1	365.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400K3-532AXSP08	262.3	406.3	311.3	349.5	-	261.2	401.9	308.4	345.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400K3-625AXSP08	301.8	457.8	354.4	395.5	743.5	300.3	451.8	351.1	390.7	730.7	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400K3-632AXSP08	286.4	439.2	338.8	378.5	720.3	285.2	434.1	335.4	374.5	708.4	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400K9-425AXSP08	254.4	395.7	302.7	339.8	-	253.2	391	299.7	336.2	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400K9-432AXSP08	235.8	369.6	281.6	316.7	-	235	365.5	279	313.5	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400K9-525AXSP08	279.5	429.1	330.3	369.8	-	278	424.3	327.1	365.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400K9-532AXSP08	262.3	406.3	311.3	349.5	-	261.2	401.9	308.4	345.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400K9-625AXSP08	301.8	457.8	354.4	395.5	743.5	300.3	451.8	351.1	390.7	730.7	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400K9-632AXSP08	286.4	439.2	338.8	378.5	720.3	285.2	434.1	335.4	374.5	708.4	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400R3-425AXSP08	259.4	403.9	308.8	346.7	-	258.3	399.3	306.3	343.1	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400R3-432AXSP08	240.5	376.7	287.3	323.2	-	239.8	372.7	284.8	320.1	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB400R3-525AXSP08	284.8	438.3	337.2	377.1	-	283.5	433	334.1	373.4	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400R3-532AXSP08	267.4	414.6	317.9	356.6	-	266.5	413.3	315.2	352.7	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB400R3-625AXSP08	307.8	467.1	361.5	403.5	-	306	461.3	357.8	398.7	746.2	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB400R3-632AXSP08	292.4	448.6	345.4	386.5	735.9	290.8	443	342.5	382	723.2	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550B3-425AXSP06	272.4	431.6	327.4	369.8	-	273.2	428.5	326.3	367	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550B3-432AXSP08	261.6	411.2	312.9	352.6	-	260.7	407.2	310.5	349.5	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB550B3-525AXSP08	311.5	480.4	369.1	413.8	-	310.5	475.1	366.1	409.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550B3-532AXSP08	292	453.9	347.6	390.2	-	290.9	449	344.4	386.4	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550B3-625AXSP08	337	512.8	396.5	442.9	-	335.6	507.2	393.1	437.9	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550B3-632AXSP08	320.1	492.1	378.4	423.9	-	318.3	486.4	375.2	419.4	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550C2-425AXSP06	284.4	451.9	342.7	386.7	-	285.2	448.5	340.9	384.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550C2-432AXSP06	261.8	419.1	316.3	357.7	-	262.6	415.8	315.2	355.4	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550C2-525AXSP06	318.5	500.2	381.5	429.5	835.2	319.1	496.5	379.5	426.3	822.3	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB550C2-532AXSP08	305.4	475.9	363.2	408.7	-	304.1	470.5	360.2	404.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550C2-625AXSP08	355.7	543.1	419.3	468.7	-	353.9	536.4	415.3	463.3	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550C2-632AXSP08	336.2	518	397.7	445.8	-	334.3	511.8	394.1	440.8	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550C2-425AXSP06	284.4	451.9	342.7	386.7	-	285.2	448.5	340.9	384.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550C2-432AXSP06	261.8	419.1	316.3	357.7	-	262.6	415.8	315.2	355.4	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550C2-525AXSP06	318.5	500.2	381.5	429.5	835.2	319.1	496.5	379.5	426.3	822.3	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB550C2-532AXSP08	305.4	475.9	363.2	408.7	-	304.1	470.5	360.2	404.5	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550C2-625AXSP08	355.7	543.1	419.3	468.7	-	353.9	536.4	415.3	463.3	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550C2-632AXSP08	336.2	518	397.7	445.8	-	334.3	511.8	394.1	440.8	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550C3-425AXSP06	284.4	451.9	342.7	386.7	-	285.2	448.5</												

EAW-VD1554ZB550K4-432AXSP08	262.5	412.7	313.5	353.2	-	261.6	408	311.6	350.2	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB550K4-525AXSP08	312.5	482	370.3	415.2	-	311.4	477.2	367.2	410.8	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K4-532AXSP08	292.4	455.5	348.1	390.9	-	291.3	450.5	345.5	387	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K4-625AXSP08	338.5	515.9	398.8	445	-	337.2	509.7	395.1	440	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550K4-632AXSP08	321.1	493.8	379.7	425.3	-	319.7	487.9	376.3	420.6	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550K5-425AXSP06	273.2	433	328.4	370.3	-	273.6	429.2	326.8	368.2	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550K5-432AXSP08	262.5	412.7	313.5	353.2	-	261.6	408	311.6	350.2	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB550K5-525AXSP08	312.5	482	370.3	415.2	-	311.4	477.2	367.2	410.8	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K5-532AXSP08	292.4	455.5	348.1	390.9	-	291.3	450.5	345.5	387	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K5-625AXSP08	338.5	515.9	398.8	445	-	337.2	509.7	395.1	440	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550K5-632AXSP08	321.1	493.8	379.7	425.3	-	319.7	487.9	376.3	420.6	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550K8-425AXSP06	273.2	433	328.4	370.3	-	273.6	429.2	326.8	368.2	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550K8-432AXSP08	262.5	412.7	313.5	353.2	-	261.6	408	311.6	350.2	-	304	27.6	3"	244	18.3	3"	365	38.7	3"
EAW-VD1554ZB550K8-525AXSP08	312.5	482	370.3	415.2	-	311.4	477.2	367.2	410.8	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K8-532AXSP08	292.4	455.5	348.1	390.9	-	291.3	450.5	345.5	387	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K8-625AXSP08	338.5	515.9	398.8	445	-	337.2	509.7	395.1	440	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550K8-632AXSP08	321.1	493.8	379.7	425.3	-	319.7	487.9	376.3	420.6	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550K9-425AXSP06	280.3	444.9	337.1	380.9	-	280.8	441.9	336.2	378.2	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550K9-432AXSP06	258.4	413.8	312.5	353.3	-	259.2	410.9	311.6	351.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB550K9-525AXSP08	321.3	496.1	380.8	426.4	-	319.8	490.6	377.8	422.1	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550K9-532AXSP08	300.6	468	357.4	402.1	-	299.5	463.1	354.8	397.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB550R3-625AXSP08	347.7	530.5	409.8	457.4	-	346.3	524.6	406.4	452.7	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB550R3-632AXSP08	329.6	507.4	390.4	436.8	-	328.3	502.3	387	432.8	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C2-425AXSP06	304.8	484.8	367.2	414.8	-	305.2	481.3	366	412.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C2-432AXSP06	280.6	449.9	339.1	383.8	-	281.2	446.2	338.2	381.9	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C2-525AXSP06	341.3	537	408.6	460.5	-	342.1	532.5	407.2	457.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C2-532AXSP06	318	504.8	383	432.5	-	318.6	501.5	382	429.5	839.7	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C2-625AXSP08	379.8	582	448.6	501.8	-	378.6	575.9	445.1	496.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C2-632AXSP08	359.2	555.1	425.9	477.7	-	357.8	549.4	422.8	473.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C3-425AXSP06	304.8	484.8	367.2	414.8	-	305.2	481.3	366	412.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C3-432AXSP06	280.6	449.9	339.1	383.8	-	281.2	446.2	338.2	381.9	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C3-525AXSP06	341.3	537	408.6	460.5	-	342.1	532.5	407.2	457.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C3-532AXSP06	318	504.8	383	432.5	-	318.6	501.5	382	429.5	839.7	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C3-625AXSP08	379.8	582	448.6	501.8	-	378.6	575.9	445.1	496.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C3-632AXSP08	359.2	555.1	425.9	477.7	-	357.8	549.4	422.8	473.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C4-425AXSP06	304.8	484.8	367.2	414.8	-	305.2	481.3	366	412.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C4-432AXSP06	280.6	449.9	339.1	383.8	-	281.2	446.2	338.2	381.9	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C4-525AXSP06	341.3	537	408.6	460.5	-	342.1	532.5	407.2	457.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C4-532AXSP06	318	504.8	383	432.5	-	318.6	501.5	382	429.5	839.7	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C4-625AXSP08	379.8	582	448.6	501.8	-	378.6	575.9	445.1	496.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C4-632AXSP08	359.2	555.1	425.9	477.7	-	357.8	549.4	422.8	473.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C5-425AXSP06	304.8	484.8	367.2	414.8	-	305.2	481.3	366	412.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C5-432AXSP06	280.6	449.9	339.1	383.8	-	281.2	446.2	338.2	381.9	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C5-525AXSP06	341.3	537	408.6	460.5	-	342.1	532.5	407.2	457.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C5-532AXSP06	318	504.8	383	432.5	-	318.6	501.5	382	429.5	839.7	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C5-625AXSP08	379.8	582	448.6	501.8	-	378.6	575.9	445.1	496.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C5-632AXSP08	359.2	555.1	425.9	477.7	-	357.8	549.4	422.8	473.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C8-425AXSP06	304.8	484.8	367.2	414.8	-	305.2	481.3	366	412.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C8-432AXSP06	280.6	449.9	339.1	383.8	-	281.2	446.2	338.2	381.9	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C8-525AXSP06	341.3	537	408.6	460.5	-	342.1	532.5	407.2	457.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C8-532AXSP06	318	504.8	383	432.5	-	318.6	501.5	382	429.5	839.7	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C8-625AXSP08	379.8	582	448.6	501.8	-	378.6	575.9	445.1	496.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C8-632AXSP08	359.2	555.1	425.9	477.7	-	357.8	549.4	422.8	473.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C9-425AXSP06	304.8	484.8	367.2	414.8	-	305.2	481.3	366	412.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C9-432AXSP06	280.6	449.9	339.1	383.8	-	281.2	446.2	338.2	381.9	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750C9-525AXSP06	341.3	537	408.6	460.5	-	342.1	532.5	407.2	457.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C9-532AXSP06	318	504.8	383	432.5	-	318.6	501.5	382	429.5	839.7	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750C9-625AXSP08	379.8	582	448.6	501.8	-	378.6	575.9	445.1	496.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750C9-632AXSP08	359.2	555.1	425.9	477.7	-	357.8	549.4	422.8	473.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750K2-425AXSP06	295	469	355.1	400.9	-	295.8	465.5	353.9	398.5	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750K2-432AXSP06	272.1	435.6	328.7	372.1	-	273	432.9	327.5	370.3	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750K2-525AXSP06	329.4	517.4	394.8	444	-	330.5	513.6	392.7	441.2	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750K2-532AXSP08	315.9	493.3	376.6	423.3	-	315.2	487.7	373.5	419.6	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB750K2-625AXSP08	366.2	559.6	431.7	482.7	-	365	553.9	428.5	478.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750K2-632AXSP08	347.2	535.7	410.9	460.7	-	345.7	530	407.7	456.2	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750K3-425AXSP06	295	469	355.1	400.9</															

EAW-VD1554ZB750R3-425AXSP06	288.8	458.6	347.6	392.3	-	289.6	455.9	346.3	390.5	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750R3-432AXSP06	266.6	426.6	322.3	364.6	-	267.5	423.9	321	362.8	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD1554ZB750R3-525AXSP06	322.1	506	385.8	433.8	844	323	502.2	384.3	431	832	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD1554ZB750R3-532AXSP08	309.2	482.3	368.4	414.1	-	308.4	477.6	366.1	410.4	-	372	28.5	3"	298	18.8	3"	446	40	3"
EAW-VD1554ZB750R3-625AXSP08	357.8	546.3	421.8	470.8	-	356.7	540.8	418	466.4	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZB750R3-632AXSP08	339.4	523.2	402.2	450.1	-	338.4	517.6	399	445.7	-	451	29.8	3"	361	19.6	3"	541	38	4"
EAW-VD1554ZK017G7-425AXSP04	354	583.9	436.6	496.6	1006.2	358.5	581.7	437.4	495.6	994.6	609	16.5	4"	487	14	3"	730	23.2	4"
EAW-VD1554ZK017G7-432AXSP06	351.2	560.9	424	479.2	-	351.3	557.2	421.8	475.6	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK017G7-525AXSP06	435.4	683.5	521.2	586.4	-	435.2	677.9	518	581.4	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK017G7-532AXSP06	402.5	637.2	483.8	545.4	-	403	631.5	480.5	541.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK017G7-625AXSP06	475.7	738.3	565.3	634.5	-	475.2	731.5	562	629.3	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK017G7-632AXSP06	444.5	696.6	531.6	597.6	-	444	689.7	528.1	592.3	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK370C2-425AXSP06	269.5	422.4	321.9	362	-	268.8	417.6	319.4	358.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C2-432AXSP06	248.4	393.2	298.9	336.8	661.7	247.9	389.1	296.4	333.7	651.6	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C2-525AXSP08	307.2	469.6	361.9	404.5	-	304.7	463.1	357.9	399.2	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C2-532AXSP08	287.4	442.9	340.4	381.4	-	285.4	436.9	336.8	376.6	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C2-625AXSP08	332.5	501.1	389.2	433.2	-	329.5	494.1	384.2	427.5	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C2-632AXSP08	315.2	480.6	371.1	414.5	-	312.9	473.7	366.8	408.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C4-425AXSP06	269.5	422.4	321.9	362	-	268.8	417.6	319.4	358.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C4-632AXSP06	248.4	393.2	298.9	336.8	661.7	247.9	389.1	296.4	333.7	651.6	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C4-525AXSP08	307.2	469.6	361.9	404.5	-	304.7	463.1	357.9	399.2	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C4-532AXSP08	287.4	442.9	340.4	381.4	-	285.4	436.9	336.8	376.6	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C5-625AXSP08	332.5	501.1	389.2	433.2	-	329.5	494.1	384.2	427.5	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C5-632AXSP08	315.2	480.6	371.1	414.5	-	312.9	473.7	366.8	408.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C5-625AXSP06	269.5	422.4	321.9	362	-	268.8	417.6	319.4	358.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C5-432AXSP06	248.4	393.2	298.9	336.8	661.7	247.9	389.1	296.4	333.7	651.6	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C5-525AXSP08	307.2	469.6	361.9	404.5	-	304.7	463.1	357.9	399.2	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C5-532AXSP08	287.4	442.9	340.4	381.4	-	285.4	436.9	336.8	376.6	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C5-625AXSP08	332.5	501.1	389.2	433.2	-	329.5	494.1	384.2	427.5	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C5-632AXSP08	315.2	480.6	371.1	414.5	-	312.9	473.7	366.8	408.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C8-425AXSP06	269.5	422.4	321.9	362	-	268.8	417.6	319.4	358.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C8-632AXSP06	248.4	393.2	298.9	336.8	661.7	247.9	389.1	296.4	333.7	651.6	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370C8-425AXSP08	307.2	469.6	361.9	404.5	-	304.7	463.1	357.9	399.2	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C8-532AXSP08	287.4	442.9	340.4	381.4	-	285.4	436.9	336.8	376.6	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370C8-625AXSP08	332.5	501.1	389.2	433.2	-	329.5	494.1	384.2	427.5	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370C8-632AXSP08	315.2	480.6	371.1	414.5	-	312.9	473.7	366.8	408.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K2-425AXSP06	259.2	406.8	310.5	349	-	259	402.3	308.1	345.5	667.7	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370K2-432AXSP08	249	387.8	296.4	332.9	-	247.8	383	293.3	329.2	-	304	30.2	3"	244	20	3"	365	42.4	3"
EAW-VD1554ZK370K2-525AXSP08	295.1	450.5	347.6	388.3	-	292.8	444.4	343.8	383.3	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K2-532AXSP08	277.1	426.3	328	367.4	-	275.2	420.7	324.2	362.8	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K2-625AXSP08	318.8	480	372.7	415.1	-	315.9	472.7	368.3	409.1	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K2-632AXSP08	302.9	460.6	356.5	398	752.2	300.7	454.1	352	392.2	738.2	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K4-425AXSP06	259.2	406.8	310.5	349	-	259	402.3	308.1	345.5	667.7	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370K4-432AXSP08	249	387.8	296.4	332.9	-	247.8	383	293.3	329.2	-	304	30.2	3"	244	20	3"	365	42.4	3"
EAW-VD1554ZK370K4-525AXSP08	295.1	450.5	347.6	388.3	-	292.8	444.4	343.8	383.3	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K4-532AXSP08	277.1	426.3	328	367.4	-	275.2	420.7	324.2	362.8	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K4-625AXSP08	318.8	480	372.7	415.1	-	315.9	472.7	368.3	409.1	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K4-632AXSP08	302.9	460.6	356.5	398	752.2	300.7	454.1	352	392.2	738.2	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K5-425AXSP06	259.2	406.8	310.5	349	-	259	402.3	308.1	345.5	667.7	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370K5-432AXSP08	249	387.8	296.4	332.9	-	247.8	383	293.3	329.2	-	304	30.2	3"	244	20	3"	365	42.4	3"
EAW-VD1554ZK370K5-525AXSP08	295.1	450.5	347.6	388.3	-	292.8	444.4	343.8	383.3	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K5-532AXSP08	277.1	426.3	328	367.4	-	275.2	420.7	324.2	362.8	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K5-625AXSP08	318.8	480	372.7	415.1	-	315.9	472.7	368.3	409.1	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K5-632AXSP08	302.9	460.6	356.5	398	752.2	300.7	454.1	352	392.2	738.2	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K8-425AXSP06	259.2	406.8	310.5	349	-	259	402.3	308.1	345.5	667.7	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK370K8-432AXSP08	249	387.8	296.4	332.9	-	247.8	383	293.3	329.2	-	304	30.2	3"	244	20	3"	365	42.4	3"
EAW-VD1554ZK370K8-525AXSP08	295.1	450.5	347.6	388.3	-	292.8	444.4	343.8	383.3	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K8-532AXSP08	277.1	426.3	328	367.4	-	275.2	420.7	324.2	362.8	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK370K8-625AXSP08	318.8	480	372.7	415.1	-	315.9	472.7	368.3	409.1	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK370K8-632AXSP08	302.9	460.6	356.5	398	752.2	300.7	454.1	352	392.2	738.2	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK400B3-425AXSP06	263.3	412.8	314.4	354.1	-	262.8	408.3	312.6	350.6	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK400B3-432AXSP08	252.3	393.3	300.4	337.5	-	247.2	387.0	297.3	333.7	-	304	30.2	3"	244	20	3"	365	42.4	3"
EAW-VD1554ZK400B3-525AXSP08	299.3	457.1	352.5	393.9	-	297	450.4	348.8	388.9	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK400B3-532AXSP08	281	432.7	332.2	372.2	-	279.2	427	328.9	367.7	-	372	31.1	3"	298	20.6	3"	446	43.7	3"
EAW-VD1554ZK400B3-625AXSP08	323.2	486.8	378.3	421	-	320.4													

EAW-VD1554ZK550B3-632AXSP08	339.2	518.5	399.6	446.6	-	336.8	511.2	395.6	441.2	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550C2-425AXSP06	302.4	476.3	361.9	407.8	-	302.2	471.3	359.5	404	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C2-432AXSP06	278.2	441.3	334.3	377.5	-	278	437.1	332.5	374.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C2-525AXSP06	338.8	527.4	403.4	453	-	338.2	521.2	400.6	448.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C2-525AXSP06	315.6	496.2	378.2	425.4	829.2	315	490.7	375.4	421.2	815.4	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C2-625AXSP06	365.3	563.3	433.5	485.1	923.5	364.6	556.6	430.1	480.4	907.2	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK550C2-632AXSP08	355.7	543.9	419.2	468.7	-	353	536.6	414.7	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550C3-425AXSP06	302.4	476.3	361.9	407.8	-	302.2	471.3	359.5	404	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C3-432AXSP06	278.2	441.3	334.3	377.5	-	278	437.1	332.5	374.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C3-525AXSP06	338.8	527.4	403.4	453	-	338.2	521.2	400.6	448.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C3-532AXSP06	315.6	496.2	378.2	425.4	829.2	315	490.7	375.4	421.2	815.4	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C3-625AXSP06	365.3	563.3	433.5	485.1	923.5	364.6	556.6	430.1	480.4	907.2	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK550C3-632AXSP08	355.7	543.9	419.2	468.7	-	353	536.6	414.7	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550C4-425AXSP06	302.4	476.3	361.9	407.8	-	302.2	471.3	359.5	404	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C4-432AXSP06	278.2	441.3	334.3	377.5	-	278	437.1	332.5	374.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C4-525AXSP06	338.8	527.4	403.4	453	-	338.2	521.2	400.6	448.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C4-532AXSP06	315.6	496.2	378.2	425.4	829.2	315	490.7	375.4	421.2	815.4	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C4-625AXSP06	365.3	563.3	433.5	485.1	923.5	364.6	556.6	430.1	480.4	907.2	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK550C4-632AXSP08	355.7	543.9	419.2	468.7	-	353	536.6	414.7	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550C5-425AXSP06	302.4	476.3	361.9	407.8	-	302.2	471.3	359.5	404	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C5-432AXSP06	278.2	441.3	334.3	377.5	-	278	437.1	332.5	374.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C5-525AXSP06	338.8	527.4	403.4	453	-	338.2	521.2	400.6	448.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C5-532AXSP06	315.6	496.2	378.2	425.4	829.2	315	490.7	375.4	421.2	815.4	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C5-625AXSP06	365.3	563.3	433.5	485.1	923.5	364.6	556.6	430.1	480.4	907.2	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK550C5-632AXSP08	355.7	543.9	419.2	468.7	-	353	536.6	414.7	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550C8-425AXSP06	302.4	476.3	361.9	407.8	-	302.2	471.3	359.5	404	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C8-432AXSP06	278.2	441.3	334.3	377.5	-	278	437.1	332.5	374.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C8-525AXSP06	338.8	527.4	403.4	453	-	338.2	521.2	400.6	448.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C8-532AXSP06	315.6	496.2	378.2	425.4	829.2	315	490.7	375.4	421.2	815.4	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C8-625AXSP06	365.3	563.3	433.5	485.1	923.5	364.6	556.6	430.1	480.4	907.2	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK550C8-632AXSP08	355.7	543.9	419.2	468.7	-	353	536.6	414.7	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550C8-632AXSP08	302.4	476.3	361.9	407.8	-	302.2	471.3	359.5	404	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C9-432AXSP06	278.2	441.3	334.3	377.5	-	278	437.1	332.5	374.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550C9-525AXSP06	338.8	527.4	403.4	453	-	338.2	521.2	400.6	448.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C9-632AXSP06	315.6	496.2	378.2	425.4	829.2	315	490.7	375.4	421.2	815.4	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550C9-625AXSP06	365.3	563.3	433.5	485.1	923.5	364.6	556.6	430.1	480.4	907.2	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK550K2-425AXSP06	290.2	456.8	347.6	391.4	-	290	452.2	345.4	388	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K2-432AXSP06	268.4	425.4	322.3	363.7	-	268.3	421.6	320.7	360.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K2-525AXSP06	323.8	503	385.3	432.4	832.6	323.3	498	382.8	428.6	819	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K2-532AXSP06	302.6	475.5	362.4	408	793.5	302.6	470.4	360.4	404.1	780.6	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K2-625AXSP08	358.8	542.6	420.8	469.2	-	356	535.5	415.8	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K2-632AXSP08	339.8	519.5	400.9	448	-	337.9	512.8	396.3	442.6	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K3-425AXSP06	290.2	456.8	347.6	391.4	-	290	452.2	345.4	388	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K3-432AXSP06	268.4	425.4	322.3	363.7	-	268.3	421.6	320.7	360.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K3-525AXSP06	323.8	503	385.3	432.4	832.6	323.3	498	382.8	428.6	819	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K3-532AXSP06	302.6	475.5	362.4	408	793.5	302.6	470.4	360.4	404.1	780.6	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K3-625AXSP08	358.8	542.6	420.8	469.2	-	356	535.5	415.8	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K3-632AXSP08	339.8	519.5	400.9	448	-	337.9	512.8	396.3	442.6	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K4-425AXSP06	290.2	456.8	347.6	391.4	-	290	452.2	345.4	388	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K4-432AXSP06	268.4	425.4	322.3	363.7	-	268.3	421.6	320.7	360.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K4-525AXSP06	323.8	503	385.3	432.4	832.6	323.3	498	382.8	428.6	819	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K4-532AXSP06	302.6	475.5	362.4	408	793.5	302.6	470.4	360.4	404.1	780.6	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K4-625AXSP08	358.8	542.6	420.8	469.2	-	356	535.5	415.8	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K4-632AXSP08	339.8	519.5	400.9	448	-	337.9	512.8	396.3	442.6	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K5-425AXSP06	290.2	456.8	347.6	391.4	-	290	452.2	345.4	388	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K5-525AXSP06	268.4	425.4	322.3	363.7	-	268.3	421.6	320.7	360.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K5-625AXSP06	323.8	503	385.3	432.4	832.6	323.3	498	382.8	428.6	819	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K5-632AXSP08	302.6	475.5	362.4	408	793.5	302.6	470.4	360.4	404.1	780.6	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K8-425AXSP06	290.2	456.8	347.6	391.4	-	290	452.2	345.4	388	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K8-432AXSP06	268.4	425.4	322.3	363.7	-	268.3	421.6	320.7	360.9	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD1554ZK550K8-525AXSP06	323.8	503	385.3	432.4	832.6	323.3	498	382.8	428.6	819	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K8-532AXSP06	302.6	475.5	362.4	408	793.5	302.6	470.4	360.4	404.1	780.6	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD1554ZK550K8-625AXSP08	358.8	542.6	420.8	469.2	-	356	535.5	415.8	462.8	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K8-632AXSP08	339.8	519.5	400.9	448	-	337.9	512.8	396.3	442.6	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD1554ZK550K9-425AXSP06	290.2	456.8	347.6	391.4	-	290	452.2	345.4	388	-	406	24.5	3"</						

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1554ZK750C5-625AXSP06	393.2	606.3	466.3	522.2	996.7	392.7	600.1	462.9	517.3	981.7	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750C5-632AXSP06	370.6	578.2	442.7	496.5	958.6	-	370.4	572.2	439.5	943.6	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD1554ZK750C8-425AXSP06	324.7	512.8	389.8	439	-	324.4	508.2	387.1	435.5	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750C8-432AXSP06	299	475.1	360	406.3	-	298.9	471.4	358.1	403.7	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750C8-525AXSP06	364	567.7	433.8	487.6	-	364	561.9	430.9	483.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750C8-532AXSP06	340	534.2	406.6	457.8	-	339.3	529	404.2	453.9	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750C8-625AXSP06	393.2	606.3	466.3	522.2	996.7	392.7	600.1	462.9	517.3	981.7	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750C8-632AXSP06	370.6	578.2	442.7	496.5	958.6	370.4	572.2	439.5	492.5	943.6	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750C9-425AXSP06	324.7	512.8	389.8	439	-	324.4	508.2	387.1	435.5	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750C9-432AXSP06	299	475.1	360	406.3	-	298.9	471.4	358.1	403.7	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750C9-525AXSP06	364	567.7	433.8	487.6	-	364	561.9	430.9	483.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750C9-532AXSP06	340	534.2	406.6	457.8	-	339.3	529	404.2	453.9	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750C9-625AXSP06	393.2	606.3	466.3	522.2	996.7	392.7	600.1	462.9	517.3	981.7	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750C9-632AXSP06	370.6	578.2	442.7	496.5	958.6	370.4	572.2	439.5	492.5	943.6	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K2-425AXSP06	314.4	495.6	377.2	424.6	-	314.2	491.3	374.7	421.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K2-432AXSP06	290.4	460.8	349.1	394.5	-	290.1	457.3	347.2	391.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K2-525AXSP06	351.9	547.8	418.5	470.1	-	351.2	542.2	416.3	466.6	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K2-532AXSP06	328.4	516.7	393.2	442.5	-	328.4	511.8	390.9	438.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K2-625AXSP06	378.4	583.4	449.2	502.8	958.3	378.1	577.9	445.6	497.9	942.5	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K2-632AXSP06	357.8	557.3	427.2	479.5	924.2	357.5	552.2	424.1	475	909.8	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K3-425AXSP06	314.4	495.6	377.2	424.6	-	314.2	491.3	374.7	421.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K3-432AXSP06	290.4	460.8	349.1	394.5	-	290.1	457.3	347.2	391.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K3-525AXSP06	351.9	547.8	418.5	470.1	-	351.2	542.2	416.3	466.6	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K3-532AXSP06	328.4	516.7	393.2	442.5	-	328.4	511.8	390.9	438.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K3-625AXSP06	378.4	583.4	449.2	502.8	958.3	378.1	577.9	445.6	497.9	942.5	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K3-632AXSP06	357.8	557.3	427.2	479.5	924.2	357.5	552.2	424.1	475	909.8	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K4-425AXSP06	314.4	495.6	377.2	424.6	-	314.2	491.3	374.7	421.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K4-432AXSP06	290.4	460.8	349.1	394.5	-	290.1	457.3	347.2	391.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K4-525AXSP06	351.9	547.8	418.5	470.1	-	351.2	542.2	416.3	466.6	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K4-532AXSP06	328.4	516.7	393.2	442.5	-	328.4	511.8	390.9	438.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K4-625AXSP06	378.4	583.4	449.2	502.8	958.3	378.1	577.9	445.6	497.9	942.5	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K4-632AXSP06	357.8	557.3	427.2	479.5	924.2	357.5	552.2	424.1	475	909.8	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K5-425AXSP06	314.4	495.6	377.2	424.6	-	314.2	491.3	374.7	421.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K5-432AXSP06	290.4	460.8	349.1	394.5	-	290.1	457.3	347.2	391.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K5-470.1	351.9	547.8	418.5	470.1	-	351.2	542.2	416.3	466.6	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K5-532AXSP06	328.4	516.7	393.2	442.5	-	328.4	511.8	390.9	438.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K5-625AXSP06	378.4	583.4	449.2	502.8	958.3	378.1	577.9	445.6	497.9	942.5	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K5-632AXSP06	357.8	557.3	427.2	479.5	924.2	357.5	552.2	424.1	475	909.8	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K8-425AXSP06	314.4	495.6	377.2	424.6	-	314.2	491.3	374.7	421.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K8-432AXSP06	290.4	460.8	349.1	394.5	-	290.1	457.3	347.2	391.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K8-525AXSP06	351.9	547.8	418.5	470.1	-	351.2	542.2	416.3	466.6	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K8-532AXSP06	328.4	516.7	393.2	442.5	-	328.4	511.8	390.9	438.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K8-625AXSP06	378.4	583.4	449.2	502.8	958.3	378.1	577.9	445.6	497.9	942.5	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K8-632AXSP06	357.8	557.3	427.2	479.5	924.2	357.5	552.2	424.1	475	909.8	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K9-425AXSP06	314.4	495.6	377.2	424.6	-	314.2	491.3	374.7	421.4	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K9-432AXSP06	290.4	460.8	349.1	394.5	-	290.1	457.3	347.2	391.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750K9-470.1	351.9	547.8	418.5	470.1	-	351.2	542.2	416.3	466.6	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K9-532AXSP06	328.4	516.7	393.2	442.5	-	328.4	511.8	390.9	438.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750K9-625AXSP06	378.4	583.4	449.2	502.8	958.3	378.1	577.9	445.6	497.9	942.5	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750K9-632AXSP06	357.8	557.3	427.2	479.5	924.2	357.5	552.2	424.1	475	909.8	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750R3-425AXSP06	307.9	485.5	369.3	416.2	-	308.2	481.2	366.7	412.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750R3-432AXSP06	284.6	451.3	342.2	386.5	-	284.4	447.8	340.3	383.3	-	406	24.5	3"	325	16.2	3"	487	34.4	3"	
EAW-VD1554ZK750R3-525AXSP06	344	535	409.7	460	-	343.9	529.6	406.8	455.9	-	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750R3-532AXSP06	321.5	505.3	384.8	433.6	844.9	321.4	500.4	382.5	430	832	507	26.3	3"	406	17.3	3"	609	32.2	4"	
EAW-VD1554ZK750R3-625AXSP06	369.5	569.3	438.5	490.8	934.7	369.2	563.9	435.7	486	919.3	609	23.6	4"	487	18.7	3"	730	33.2	4"	
EAW-VD1554ZK750R3-632AXSP08	360.6	552.5	425.6	476	-	358.4	545.9	421.1	470.7	-	451	32.4	3"	361	21.4	3"	541	41.7	4"	
EAW-VD1555PB370C2-425AXSP04	263.9	428.1	322	365.4	730.2	266.5	426.5	322.8	364.6	722.5	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD1555PB370C2-432AXSP06	257.7	407.8	309.3	348.8	-	257.4	404.9	307.9	346.8	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD1555PB370C2-525AXSP06	313.3	485.8	372.2	417.7	-	312.7	481.6	370.2	414.5	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD1555PB370C2-532AXSP06	294	460	351	394.7	-	293.8	456.3	348.8	391.9	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD1555PB370C2-625AXSP06	337.3	516.8	398.2	445.3	-	336.9	512.5	396	441.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD1555PB370C2-632AXSP06	321.2	497.2	381.3	427.5	-	320.8	492.7	379	424	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD1555PB370C4-425AXSP04	263.9	428.1	322	365.4	730.2	266.5	426.5	322.8	364.6	722.5	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD1555PB370C4-432AXSP06	257.7	407.8	309.3	348.8	-	257.4	404.9	307.9	346.8	-	293	25.4								

EAW-VD155SPB370K8-52AXSP06	283.2	442.9	338	379.8	-	282.8	439.1	335.7	376.9	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB370K8-62AXSP06	324.4	496.5	382.9	428	-	324.1	491.8	380.3	424.3	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB370K8-632AXSP06	309	477.5	366.7	410.9	-	309	473.7	364.3	407.4	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400B3-425AXSP04	256.4	415.8	313.2	355.1	708.3	258.8	414.2	313.4	354.3	700.9	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB400B3-432AXSP06	251.2	397.5	301.4	340.3	-	251.1	394.3	300.1	338	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD155SPB400B3-525AXSP06	302.9	469.8	360.3	404.2	-	303	466.1	358.1	401.4	-	372	26.4	3"	301	298	17.4	3"	446	37	3"
EAW-VD155SPB400B3-532AXSP06	285.8	446.5	341.1	383.3	-	285.5	442.9	338.9	380.6	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400B3-625AXSP06	325.3	497.9	384.4	429.2	-	325.2	494.2	382.1	426.3	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400C3-625AXSP06	311.1	480.9	369.2	413.8	-	311	476.9	367.2	410.7	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400C3-425AXSP04	263.9	428.1	322	365.4	730.2	266.5	426.5	322.8	364.6	722.5	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB400C3-432AXSP06	257.7	407.8	309.3	348.8	-	257.4	404.9	307.9	346.8	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD155SPB400C3-525AXSP06	313.3	485.8	372.2	417.7	-	312.7	481.6	370.2	414.5	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400C3-532AXSP06	294	460	351	394.7	-	293.8	456.3	348.8	391.9	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400C3-625AXSP06	337.3	516.8	398.2	445.3	-	336.9	512.5	396	441.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400C3-632AXSP06	321.2	497.2	381.3	427.5	-	320.8	492.7	379	424	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400C9-425AXSP04	263.9	428.1	322	365.4	730.2	266.5	426.5	322.8	364.6	722.5	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB400C9-432AXSP06	257.7	407.8	309.3	348.8	-	257.4	404.9	307.9	346.8	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD155SPB400C9-525AXSP06	313.3	485.8	372.2	417.7	-	312.7	481.6	370.2	414.5	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400C9-532AXSP06	294	460	351	394.7	-	293.8	456.3	348.8	391.9	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400C9-625AXSP06	337.3	516.8	398.2	445.3	-	336.9	512.5	396	441.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400C9-632AXSP06	321.2	497.2	381.3	427.5	-	320.8	492.7	379	424	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400K3-425AXSP04	253.5	411.7	310.2	351.7	702.1	256.3	410.6	310.8	350.7	693.3	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB400K3-432AXSP06	248.6	393.5	298.5	336.3	-	248.4	389.9	297	334.3	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD155SPB400K3-525AXSP06	301.3	467.1	357.8	401.4	-	301	462.9	355.7	398.2	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400K3-532AXSP06	283.2	442.9	338	379.8	-	282.8	439.1	335.7	376.9	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400K3-625AXSP06	324.4	496.5	382.9	428	-	324.1	491.8	380.3	424.3	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400K3-632AXSP06	309	477.5	366.7	410.9	-	309	473.7	364.3	407.4	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400K9-425AXSP04	253.5	411.7	310.2	351.7	702.1	256.3	410.6	310.8	350.7	693.3	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB400K9-432AXSP06	248.6	393.5	298.5	336.3	-	248.4	389.9	297	334.3	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD155SPB400K9-525AXSP06	301.3	467.1	357.8	401.4	-	301	462.9	355.7	398.2	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400K9-532AXSP06	283.2	442.9	338	379.8	-	282.8	439.1	335.7	376.9	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400K9-625AXSP06	324.4	496.5	382.9	428	-	324.1	491.8	380.3	424.3	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400K9-632AXSP06	309	477.5	366.7	410.9	-	309	473.7	364.3	407.4	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400R3-425AXSP04	258.1	418.8	315.3	357.6	713.7	261.1	418	316.1	356.8	706.2	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB400R3-432AXSP06	252.9	400	303.7	342.4	-	252.7	397.3	301.8	339.8	-	293	25.4	3"	234	21.1	2"	352	35.6	3"	
EAW-VD155SPB400R3-525AXSP06	306	474.8	363.5	407.9	-	305.9	470.7	361.5	404.8	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400R3-532AXSP06	287.8	449.8	343.5	386.1	-	287.6	446.2	341.3	383.4	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB400R3-625AXSP06	329.7	504.9	389.2	435.1	-	329.1	500.3	386.7	431.5	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB400R3-632AXSP06	314.3	485.3	372.4	417.5	-	313.9	481.6	370.2	414.7	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB50B3-425AXSP04	280.1	454.5	341.4	387.2	-	283.3	453.6	342.3	387	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB50B3-432AXSP04	258.1	423.6	317.3	360.5	728.4	261.3	422.4	317.9	359.9	720.8	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB50B3-432AXSP06	330.8	514.4	393.3	441.8	-	330.9	511.1	392.1	439.4	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB50B3-532AXSP06	310.8	488.1	371.6	418.2	-	311.2	484.1	369.8	415.8	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB50B3-625AXSP06	355	545.2	420	469.8	-	355.5	541.8	418	467.4	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB50B3-632AXSP06	339.3	525.8	403.1	452.3	-	339.2	522.2	400.9	449.6	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C2-425AXSP04	295.2	478.2	359.6	407.5	-	298.3	477	359.7	407.1	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C2-432AXSP04	270.8	443	331.9	377.6	-	273.8	442.4	332.5	377	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C2-525AXSP04	328.4	528.5	399.8	451.6	894.9	332.2	527.2	400.5	451.2	884.6	564	17.8	4"	451	14.3	3"	676	25	4"	
EAW-VD155SPB550C2-532AXSP06	327.3	514.7	391.6	441.1	-	327.5	510.2	389.5	437.7	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB550C2-625AXSP06	379.1	583.5	448.7	502.4	-	378.5	579	446.5	498.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C2-632AXSP06	359.1	558	426.9	479.4	-	359.4	553.8	425	476.2	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C3-425AXSP04	295.2	478.2	359.6	407.5	-	298.3	477	359.7	407.1	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C3-432AXSP04	270.8	443	331.9	377.6	-	273.8	442.4	332.5	377	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C3-432AXSP06	328.4	528.5	399.8	451.6	894.9	332.2	527.2	400.5	451.2	884.6	564	17.8	4"	451	14.3	3"	676	25	4"	
EAW-VD155SPB550C3-532AXSP06	327.3	514.7	391.6	441.1	-	327.5	510.2	389.5	437.7	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB550C3-625AXSP06	379.1	583.5	448.7	502.4	-	378.5	579	446.5	498.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C3-632AXSP06	359.1	558	426.9	479.4	-	359.4	553.8	425	476.2	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C4-425AXSP04	295.2	478.2	359.6	407.5	-	298.3	477	359.7	407.1	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C4-432AXSP04	270.8	443	331.9	377.6	-	273.8	442.4	332.5	377	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C4-525AXSP04	328.4	528.5	399.8	451.6	894.9	332.2	527.2	400.5	451.2	884.6	564	17.8	4"	451	14.3	3"	676	25	4"	
EAW-VD155SPB550C4-532AXSP06	327.3	514.7	391.6	441.1	-	327.5	510.2	389.5	437.7	-	372	26.4	3"	298	17.4	3"	446	37	3"	
EAW-VD155SPB550C4-625AXSP06	379.1	583.5	448.7	502.4	-	378.5	579	446.5	498.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C4-632AXSP06	359.1	558	426.9	479.4	-	359.4	553.8	425	476.2	-	451	27.6	3"	361	18.2	3"	541	35.1	4"	
EAW-VD155SPB550C5-425AXSP04	295.2	478.2	359.6	407.5	-	298.3	477	359.7	407.1	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C5-432AXSP04	270.8	443	331.9	377.6	-	273.8	442.4	332.5	377	-	451	19.6	3"	361	12.9	3"	541	24	4"	
EAW-VD155SPB550C5-525AXSP04	328.4	528.																		

EAW-VD155SPB550K5-525AXSP04	312	503	380.1	429.7	848.8	315.5	500.9	381.2	429.2	840.2	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB550K5-532AXSP06	313	490.8	374.2	421.1	-	312.7	487.4	372.2	417.9	-	372	26.4	3"	298	17.4	3"	446	37	3"
EAW-VD155SPB550K5-625AXSP06	360.4	553.6	425.7	477	-	360.1	549.1	423.5	473.5	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550K5-632AXSP06	342.1	531.1	406.4	456.1	-	342.1	526.9	404.4	452.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550K8-425AXSP04	281.8	456.7	343.6	389.7	-	284.9	455.6	344.4	389.4	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB550K8-432AXSP04	259.3	425.3	318.5	362	730.3	262.2	423.9	319	361.2	723.5	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB550K8-525AXSP04	312	503	380.1	429.7	848.8	315.5	500.9	381.2	429.2	840.2	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB550K8-532AXSP06	313	490.8	374.2	421.1	-	312.7	487.4	372.2	417.9	-	372	26.4	3"	298	17.4	3"	446	37	3"
EAW-VD155SPB550K8-625AXSP06	360.4	553.6	425.7	477	-	360.1	549.1	423.5	473.5	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550K8-632AXSP06	342.1	531.1	406.4	456.1	-	342.1	526.9	404.4	452.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550K9-425AXSP04	281.8	456.7	343.6	389.7	-	284.9	455.6	344.4	389.4	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB550K9-432AXSP04	259.3	425.3	318.5	362	730.3	262.2	423.9	319	361.2	723.5	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB550K9-525AXSP04	312	503	380.1	429.7	848.8	315.5	500.9	381.2	429.2	840.2	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB550K9-532AXSP06	313	490.8	374.2	421.1	-	312.7	487.4	372.2	417.9	-	372	26.4	3"	298	17.4	3"	446	37	3"
EAW-VD155SPB550K9-625AXSP06	360.4	553.6	425.7	477	-	360.1	549.1	423.5	473.5	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550K9-632AXSP06	342.1	531.1	406.4	456.1	-	342.1	526.9	404.4	452.9	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550R3-425AXSP04	288.8	467.9	351.6	399	-	291.6	467	352.6	398.9	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB550R3-432AXSP04	265.7	435	325.9	370.6	749.3	268.8	434.6	326.6	370.1	741.4	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB550R3-525AXSP04	319.6	515.2	389.6	440.6	870.2	323.4	513.3	390.3	439.6	861.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB550R3-532AXSP06	320.2	502.8	382.9	431.2	-	320	498.8	381.1	428.1	-	372	26.4	3"	298	17.4	3"	446	37	3"
EAW-VD155SPB550R3-625AXSP06	368.7	567	436.3	488.3	-	368.6	562.6	434.2	485	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB550R3-632AXSP06	350.5	543.9	416.5	467.6	-	350.2	539.8	414.7	464.5	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C2-425AXSP04	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C2-432AXSP04	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C2-432AXSP04	346.9	558.3	421.3	477.2	-	351.1	557.3	423	477	938.4	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C2-532AXSP04	323.6	526.8	396	449	899.4	327.5	526.1	397.2	449	891.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C2-625AXSP04	370.7	593.2	450.4	507.6	994.3	375.7	591.9	451.6	507.8	985.3	676	18.6	4"	541	12.3	4"	812	26.2	4"
EAW-VD155SPB750C2-632AXSP06	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C3-425AXSP04	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C3-432AXSP04	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C3-432AXSP04	346.9	558.3	421.3	477.2	-	351.1	557.3	423	477	938.4	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C3-525AXSP04	323.6	526.8	396	449	899.4	327.5	526.1	397.2	449	891.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C3-532AXSP04	370.7	593.2	450.4	507.6	994.3	375.7	591.9	451.6	507.8	985.3	676	18.6	4"	541	12.3	4"	812	26.2	4"
EAW-VD155SPB750C3-632AXSP06	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C4-425AXSP04	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C4-432AXSP04	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C4-432AXSP04	346.9	558.3	421.3	477.2	-	351.1	557.3	423	477	938.4	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C4-532AXSP04	323.6	526.8	396	449	899.4	327.5	526.1	397.2	449	891.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C4-625AXSP04	370.7	593.2	450.4	507.6	994.3	375.7	591.9	451.6	507.8	985.3	676	18.6	4"	541	12.3	4"	812	26.2	4"
EAW-VD155SPB750C4-632AXSP06	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C5-425AXSP04	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C5-432AXSP04	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C5-432AXSP04	346.9	558.3	421.3	477.2	-	351.1	557.3	423	477	938.4	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C5-525AXSP04	323.6	526.8	396	449	899.4	327.5	526.1	397.2	449	891.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C5-532AXSP04	370.7	593.2	450.4	507.6	994.3	375.7	591.9	451.6	507.8	985.3	676	18.6	4"	541	12.3	4"	812	26.2	4"
EAW-VD155SPB750C5-625AXSP04	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C5-632AXSP06	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C8-425AXSP04	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C8-432AXSP04	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C8-432AXSP04	346.9	558.3	421.3	477.2	-	351.1	557.3	423	477	938.4	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C8-525AXSP04	323.6	526.8	396	449	899.4	327.5	526.1	397.2	449	891.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C8-532AXSP04	370.7	593.2	450.4	507.6	994.3	375.7	591.9	451.6	507.8	985.3	676	18.6	4"	541	12.3	4"	812	26.2	4"
EAW-VD155SPB750C8-625AXSP04	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C8-632AXSP06	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C9-425AXSP04	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C9-432AXSP04	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C9-525AXSP04	346.9	558.3	421.3	477.2	-	351.1	557.3	423	477	938.4	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C9-532AXSP04	323.6	526.8	396	449	899.4	327.5	526.1	397.2	449	891.8	564	17.8	4"	451	14.3	3"	676	25	4"
EAW-VD155SPB750C9-625AXSP04	370.7	593.2	450.4	507.6	994.3	375.7	591.9	451.6	507.8	985.3	676	18.6	4"	541	12.3	4"	812	26.2	4"
EAW-VD155SPB750C9-632AXSP06	378.6	589.1	450.4	506.2	-	379	585.6	449.3	503.8	-	451	27.6	3"	361	18.2	3"	541	35.1	4"
EAW-VD155SPB750C9-632AXSP06	312.2	506.7	380.4	431.8	-	315.6	505.6	381.5	431.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750C9-632AXSP06	287.2	469.8	351.6	399.8	-	290.6	469.4	352.6	400	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750K2-425AXSP04	302.1	489.9	367.9	417.1	-	305.6	489.5	368.7	417.5	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750K2-432AXSP04	278.3	455	340.7	387.4	-	281.5	454.5	342.1	387.7	-	451	19.6	3"	361	12.9	3"	541	24	4"
EAW-VD155SPB750K2-525AXSP04	335.2	539.2	407.6	460.5	912.5	339	538.6	408.8	460.7	904.4	564	17							

EAW-VD155SP1370C2-432AXSP04	293.9	466.1	353.6	399.1	-	293.8	461.8	351.2	395.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C2-525AXSP04	355	551.7	422.5	474.2	914.5	354.5	546.4	419.8	470.1	899.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C2-532AXSP04	331.9	521.8	397.6	447.6	871	331.3	516.1	395.3	443.3	856.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C2-625AXSP04	380.5	587.5	452.6	506.3	961.4	380.4	580.8	449.3	500.9	946	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C2-632AXSP04	360.1	562.4	430.9	484	929.7	360	556.8	428	479	914.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C4-425AXSP04	318.1	501	381.2	429.3	-	317.9	495.9	378.7	425.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C4-432AXSP04	293.9	466.1	353.6	399.1	-	293.8	461.8	351.2	395.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C4-532AXSP04	355	551.7	422.5	474.2	914.5	354.5	546.4	419.8	470.1	899.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C4-532AXSP04	331.9	521.8	397.6	447.6	871	331.3	516.1	395.3	443.3	856.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C4-625AXSP04	380.5	587.5	452.6	506.3	961.4	380.4	580.8	449.3	500.9	946	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C4-632AXSP04	360.1	562.4	430.9	484	929.7	360	556.8	428	479	914.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C5-425AXSP04	318.1	501	381.2	429.3	-	317.9	495.9	378.7	425.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C5-432AXSP04	293.9	466.1	353.6	399.1	-	293.8	461.8	351.2	395.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C5-525AXSP04	355	551.7	422.5	474.2	914.5	354.5	546.4	419.8	470.1	899.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C5-532AXSP04	331.9	521.8	397.6	447.6	871	331.3	516.1	395.3	443.3	856.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C5-625AXSP04	380.5	587.5	452.6	506.3	961.4	380.4	580.8	449.3	500.9	946	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C5-632AXSP04	360.1	562.4	430.9	484	929.7	360	556.8	428	479	914.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C8-425AXSP04	318.1	501	381.2	429.3	-	317.9	495.9	378.7	425.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C8-432AXSP04	293.9	466.1	353.6	399.1	-	293.8	461.8	351.2	395.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370C8-525AXSP04	355	551.7	422.5	474.2	914.5	354.5	546.4	419.8	470.1	899.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C8-532AXSP04	331.9	521.8	397.6	447.6	871	331.3	516.1	395.3	443.3	856.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370C8-625AXSP04	380.5	587.5	452.6	506.3	961.4	380.4	580.8	449.3	500.9	946	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370C8-632AXSP04	360.1	562.4	430.9	484	929.7	360	556.8	428	479	914.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K2-425AXSP04	306.5	481.7	367	413.1	-	306.3	477.7	364.7	409.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K2-432AXSP04	283.7	449.8	341.2	384.8	-	283.6	445.7	339.5	381.8	747.8	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K2-525AXSP04	340.5	529.8	405.7	455.7	876.2	340	524	403	451.2	862.1	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K2-532AXSP04	319	501.4	382.5	430.5	835.9	319	496.8	380.4	426.4	823.6	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K2-625AXSP04	364.4	562.7	433.3	485.2	919	364.3	556.2	430.1	480	904.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K2-632AXSP04	345.5	539.6	413.3	464.6	890	345.9	534.1	410.4	459.8	875.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K4-425AXSP04	306.5	481.7	367	413.1	-	306.3	477.7	364.7	409.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K4-432AXSP04	283.7	449.8	341.2	384.8	-	283.6	445.7	339.5	381.8	747.8	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K4-525AXSP04	340.5	529.8	405.7	455.7	876.2	340	524	403	451.2	862.1	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K4-532AXSP04	319	501.4	382.5	430.5	835.9	319	496.8	380.4	426.4	823.6	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K4-625AXSP04	364.4	562.7	433.3	485.2	919	364.3	556.2	430.1	480	904.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K4-632AXSP04	345.5	539.6	413.3	464.6	890	345.9	534.1	410.4	459.8	875.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K5-425AXSP04	306.5	481.7	367	413.1	-	306.3	477.7	364.7	409.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K5-432AXSP04	283.7	449.8	341.2	384.8	-	283.6	445.7	339.5	381.8	747.8	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K5-525AXSP04	340.5	529.8	405.7	455.7	876.2	340	524	403	451.2	862.1	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K5-532AXSP04	319	501.4	382.5	430.5	835.9	319	496.8	380.4	426.4	823.6	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K5-625AXSP04	364.4	562.7	433.3	485.2	919	364.3	556.2	430.1	480	904.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K5-632AXSP04	345.5	539.6	413.3	464.6	890	345.9	534.1	410.4	459.8	875.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K8-425AXSP04	306.5	481.7	367	413.1	-	306.3	477.7	364.7	409.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K8-432AXSP04	283.7	449.8	341.2	384.8	-	283.6	445.7	339.5	381.8	747.8	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1370K8-525AXSP04	340.5	529.8	405.7	455.7	876.2	340	524	403	451.2	862.1	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K8-532AXSP04	319	501.4	382.5	430.5	835.9	319	496.8	380.4	426.4	823.6	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1370K8-625AXSP04	364.4	562.7	433.3	485.2	919	364.3	556.2	430.1	480	904.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1370K8-632AXSP04	345.5	539.6	413.3	464.6	890	345.9	534.1	410.4	459.8	875.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155PI400B3-425AXSP04	310.6	488.4	372	418.7	-	310.5	483.7	369.7	415.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155PI400B3-432AXSP04	287.5	456.1	345.8	390	-	287.5	452.1	343.5	387.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155PI400B3-525AXSP04	344.9	537	411.6	461.8	888.3	345.1	531.3	408.5	457.4	874.4	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155PI400B3-532AXSP04	323.2	508.3	387.7	436.3	847.9	323.3	503.1	385.6	432.3	834.4	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155PI400B3-625AXSP04	368.7	568.8	438.5	490.3	930.2	368.8	562.7	435.5	486.1	915	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155PI400B3-632AXSP04	350.5	546.9	418.7	470.8	902.3	350.5	541.6	416	466	887.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155PI400C3-425AXSP04	318.1	501	381.2	429.3	-	317.9	495.9	378.7	425.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155PI400C3-432AXSP04	293.9	466.1	353.6	399.1	-	293.8	461.8	351.2	395.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155PI400C3-525AXSP04	355	551.7	422.5	474.2	914.5	354.5	546.4	419.8	470.1	899.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155PI400C3-532AXSP04	331.9	521.8	397.6	447.6	871	331.3	516.1	395.3	443.3	856.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155PI400C3-625AXSP04	380.5	587.5	452.6	506.3	961.4	380.4	580.8	449.3	500.9	946	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155PI400C3-632AXSP04	360.1	562.4	430.9	484	929.7	360	556.8	428	479	914.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155PI400C9-425AXSP04	318.1	501	381.2	429.3	-	317.9	495.9	378.7	425.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155PI400C9-432AXSP04	293.9	466.1	353.6	399.1	-	293.8	461.8	351.2	395.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155PI400C9-525AXSP04	355	551.7	422.5	474.2	914.5	354.5	546.4	419.8	470.1	899.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155PI400C9-532AXSP04	331.9	521.8	397.6	447.6	871	331.3	516.1	395.3	443.3	856.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155PI400C9-625AXSP04	380.5	587.5	452.6	506.3	961														

EAW-VD155SP1550C4-425AXSP04	356.5	563.4	427.3	482.2	-	356.3	558.4	425.1	478.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C4-432AXSP04	328.2	521.8	395.3	446.2	-	328.2	517.8	393.1	443.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C4-525AXSP04	400.1	624.2	476.9	536	-	399.5	617.9	473.7	531.2	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C4-532AXSP04	372.9	587.1	446.7	503	-	372.8	581.3	444	498.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C4-625AXSP04	431.9	667.1	512.2	573.7	1096.8	431.1	660	509	568.9	1079.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550C4-632AXSP04	406.8	635.8	486	545.9	1054.4	406.6	629.3	483.3	541.6	1037.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550C5-425AXSP04	356.5	563.4	427.3	482.2	-	356.3	558.4	425.1	478.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C5-432AXSP04	328.2	521.8	395.3	446.2	-	328.2	517.8	393.1	443.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C5-525AXSP04	400.1	624.2	476.9	536	-	399.5	617.9	473.7	531.2	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C5-532AXSP04	372.9	587.1	446.7	503	-	372.8	581.3	444	498.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C5-625AXSP04	431.9	667.1	512.2	573.7	1096.8	431.1	660	509	568.9	1079.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550C5-632AXSP04	406.8	635.8	486	545.9	1054.4	406.6	629.3	483.3	541.6	1037.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550C8-425AXSP04	356.5	563.4	427.3	482.2	-	356.3	558.4	425.1	478.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C8-432AXSP04	328.2	521.8	395.3	446.2	-	328.2	517.8	393.1	443.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C8-525AXSP04	400.1	624.2	476.9	536	-	399.5	617.9	473.7	531.2	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C8-532AXSP04	372.9	587.1	446.7	503	-	372.8	581.3	444	498.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C8-625AXSP04	431.9	667.1	512.2	573.7	1096.8	431.1	660	509	568.9	1079.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550C8-632AXSP04	406.8	635.8	486	545.9	1054.4	406.6	629.3	483.3	541.6	1037.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550C9-425AXSP04	356.5	563.4	427.3	482.2	-	356.3	558.4	425.1	478.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C9-432AXSP04	328.2	521.8	395.3	446.2	-	328.2	517.8	393.1	443.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550C9-525AXSP04	400.1	624.2	476.9	536	-	399.5	617.9	473.7	531.2	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C9-532AXSP04	372.9	587.1	446.7	503	-	372.8	581.3	444	498.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550C9-632AXSP04	406.8	635.8	486	545.9	1054.4	406.6	629.3	483.3	541.6	1037.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K2-425AXSP04	341.8	539.7	410.1	462.3	-	341.6	535.1	407.4	458.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K2-432AXSP04	315.7	501.5	379.9	429.3	-	315.7	497.8	377.9	425.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K2-525AXSP04	382.1	594.8	455.1	511.3	-	381.5	588.9	452.1	506.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K2-532AXSP04	357	561.7	427.5	481.8	939.9	357	556.5	425	477.9	925.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K2-625AXSP04	410.3	633.5	487.1	545.3	1040.6	410.3	627.1	484.2	541	1023.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K2-632AXSP04	388	606.1	464	520.8	1003.8	388.4	599.9	461.4	516	988.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K3-425AXSP04	341.8	539.7	410.1	462.3	-	341.6	535.1	407.4	458.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K3-432AXSP04	315.7	501.5	379.9	429.3	-	315.7	497.8	377.9	425.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K3-525AXSP04	382.1	594.8	455.1	511.3	-	381.5	588.9	452.1	506.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K3-532AXSP04	357	561.7	427.5	481.8	939.9	357	556.5	425	477.9	925.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K3-625AXSP04	410.3	633.5	487.1	545.3	1040.6	410.3	627.1	484.2	541	1023.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K3-632AXSP04	388	606.1	464	520.8	1003.8	388.4	599.9	461.4	516	988.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K4-425AXSP04	341.8	539.7	410.1	462.3	-	341.6	535.1	407.4	458.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K4-432AXSP04	315.7	501.5	379.9	429.3	-	315.7	497.8	377.9	425.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K4-525AXSP04	382.1	594.8	455.1	511.3	-	381.5	588.9	452.1	506.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K4-532AXSP04	357	561.7	427.5	481.8	939.9	357	556.5	425	477.9	925.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K4-625AXSP04	410.3	633.5	487.1	545.3	1040.6	410.3	627.1	484.2	541	1023.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K4-632AXSP04	388	606.1	464	520.8	1003.8	388.4	599.9	461.4	516	988.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K5-425AXSP04	341.8	539.7	410.1	462.3	-	341.6	535.1	407.4	458.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K5-432AXSP04	315.7	501.5	379.9	429.3	-	315.7	497.8	377.9	425.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K5-525AXSP04	382.1	594.8	455.1	511.3	-	381.5	588.9	452.1	506.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K5-532AXSP04	357	561.7	427.5	481.8	939.9	357	556.5	425	477.9	925.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K5-625AXSP04	410.3	633.5	487.1	545.3	1040.6	410.3	627.1	484.2	541	1023.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K5-632AXSP04	388	606.1	464	520.8	1003.8	388.4	599.9	461.4	516	988.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K8-425AXSP04	341.8	539.7	410.1	462.3	-	341.6	535.1	407.4	458.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K8-432AXSP04	315.7	501.5	379.9	429.3	-	315.7	497.8	377.9	425.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K8-525AXSP04	382.1	594.8	455.1	511.3	-	381.5	588.9	452.1	506.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K8-625AXSP04	357	561.7	427.5	481.8	939.9	357	556.5	425	477.9	925.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K8-632AXSP04	410.3	633.5	487.1	545.3	1040.6	410.3	627.1	484.2	541	1023.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K9-425AXSP04	388	606.1	464	520.8	1003.8	388.4	599.9	461.4	516	988.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K9-432AXSP04	341.8	539.7	410.1	462.3	-	341.6	535.1	407.4	458.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K9-525AXSP04	315.7	501.5	379.9	429.3	-	315.7	497.8	377.9	425.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550K9-532AXSP04	382.1	594.8	455.1	511.3	-	381.5	588.9	452.1	506.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K9-625AXSP04	357	561.7	427.5	481.8	939.9	357	556.5	425	477.9	925.8	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550K9-632AXSP04	410.3	633.5	487.1	545.3	1040.6	410.3	627.1	484.2	541	1023.9	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550K9-632AXSP04	388	606.1	464	520.8	1003.8	388.4	599.9	461.4	516	988.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1550R3-425AXSP04	351.2	554.5	420.8	474.7	-	351.2	550	419	471.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550R3-432AXSP04	324.2	515	390.3	440.5	-	324.4	511.4	388.5	438	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1550R3-525AXSP04	392.1	611.2	467.2	525	-	392.3	606.2	465	521.4	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550R3-532AXSP04	366.8	577	439.4	494.6	-	367	571.9	437.1	490.9	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1550R3-625AXSP04	422	651.3	500.4	561.1	1070.3	421.7	645.1	497.8	556.3	1053.9	676	23.6	4"	541	15.5	4"	812	33.1	

EAW-VD155SP1750C9-632AXSP04	436.1	680.7	519.8	584.4	-	436	674.8	517.8	580	1116.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K2-425AXSP04	368.9	583.4	443.3	499.6	-	369.3	579.1	441	496.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K2-432AXSP04	340.2	542	409.7	463.7	-	340.7	538.7	408.2	460.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K2-525AXSP04	413	645.3	492.5	553.8	-	413	639.7	489.8	549.6	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K2-532AXSP04	386	608	462	520.5	-	386	603.1	460	517	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K2-625AXSP04	444.7	686.6	527.5	591	-	444.8	680.7	524.5	586.5	1114.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K2-632AXSP04	420.3	657.1	502.5	564.6	1092	420.7	651.1	499.5	560	1076.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K3-425AXSP04	368.9	583.4	443.3	499.6	-	369.3	579.1	441	496.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K3-432AXSP04	340.2	542	409.7	463.7	-	340.7	538.7	408.2	460.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K3-525AXSP04	413	645.3	492.5	553.8	-	413	639.7	489.8	549.6	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K3-532AXSP04	386	608	462	520.5	-	386	603.1	460	517	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K3-625AXSP04	444.7	686.6	527.5	591	-	444.8	680.7	524.5	586.5	1114.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K3-632AXSP04	420.3	657.1	502.5	564.6	1092	420.7	651.1	499.5	560	1076.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K4-425AXSP04	368.9	583.4	443.3	499.6	-	369.3	579.1	441	496.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K4-432AXSP04	340.2	542	409.7	463.7	-	340.7	538.7	408.2	460.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K4-525AXSP04	413	645.3	492.5	553.8	-	413	639.7	489.8	549.6	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K4-532AXSP04	386	608	462	520.5	-	386	603.1	460	517	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K4-625AXSP04	444.7	686.6	527.5	591	-	444.8	680.7	524.5	586.5	1114.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K4-632AXSP04	420.3	657.1	502.5	564.6	1092	420.7	651.1	499.5	560	1076.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K5-425AXSP04	368.9	583.4	443.3	499.6	-	369.3	579.1	441	496.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K5-432AXSP04	340.2	542	409.7	463.7	-	340.7	538.7	408.2	460.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K5-525AXSP04	413	645.3	492.5	553.8	-	413	639.7	489.8	549.6	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K5-532AXSP04	386	608	462	520.5	-	386	603.1	460	517	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K5-625AXSP04	444.7	686.6	527.5	591	-	444.8	680.7	524.5	586.5	1114.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K5-632AXSP04	420.3	657.1	502.5	564.6	1092	420.7	651.1	499.5	560	1076.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K8-425AXSP04	368.9	583.4	443.3	499.6	-	369.3	579.1	441	496.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K8-432AXSP04	340.2	542	409.7	463.7	-	340.7	538.7	408.2	460.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K8-525AXSP04	413	645.3	492.5	553.8	-	413	639.7	489.8	549.6	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K8-532AXSP04	386	608	462	520.5	-	386	603.1	460	517	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K8-625AXSP04	444.7	686.6	527.5	591	-	444.8	680.7	524.5	586.5	1114.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K8-632AXSP04	420.3	657.1	502.5	564.6	1092	420.7	651.1	499.5	560	1076.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K9-425AXSP04	368.9	583.4	443.3	499.6	-	369.3	579.1	441	496.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K9-432AXSP04	340.2	542	409.7	463.7	-	340.7	538.7	408.2	460.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750K9-525AXSP04	413	645.3	492.5	553.8	-	413	639.7	489.8	549.6	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K9-532AXSP04	386	608	462	520.5	-	386	603.1	460	517	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750K9-625AXSP04	444.7	686.6	527.5	591	-	444.8	680.7	524.5	586.5	1114.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750K9-632AXSP04	420.3	657.1	502.5	564.6	1092	420.7	651.1	499.5	560	1076.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750R3-425AXSP04	361.2	571.4	433.9	489.6	-	361.6	567.2	431.6	485.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750R3-432AXSP04	333.7	531.7	401.6	454.4	-	334	527.5	400.1	451.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD155SP1750R3-525AXSP04	403.7	630.2	481.3	541	-	404.2	624.7	479.4	536.9	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750R3-532AXSP04	377.9	594.5	452.8	510	-	378.4	589.6	450.1	506.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD155SP1750R3-625AXSP04	434	670.5	514.8	576.6	1102.5	434.1	664.7	512.5	572.1	1086.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SP1750R3-632AXSP04	411	641.8	491.1	551.6	1065.9	411.3	635.9	488.2	547.2	1050.6	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD155SPK370C2-425AXSP04	284.2	454.8	344	389	-	286.1	452.2	343.4	387.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C2-432AXSP04	261.8	423.9	318.9	361.5	722.5	263.5	421.2	318.9	359.8	714	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C2-525AXSP04	315.8	501.3	381.5	429.6	838.5	317.6	497.9	380.3	427.3	828.2	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK370C2-532AXSP06	313.7	488.1	372.9	418.8	-	312.7	482.4	370.3	415	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD155SPK370C2-625AXSP06	360.7	549.2	424.5	474.3	-	359.5	543.5	421.2	469.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD155SPK370C2-632AXSP06	343	527.8	405.6	454.4	-	342.1	522.3	402.6	450.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD155SPK370C4-425AXSP04	284.2	454.8	344	389	-	286.1	452.2	343.4	387.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C4-432AXSP04	261.8	423.9	318.9	361.5	722.5	263.5	421.2	318.9	359.8	714	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C4-525AXSP04	315.8	501.3	381.5	429.6	838.5	317.6	497.9	380.3	427.3	828.2	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK370C4-532AXSP06	313.7	488.1	372.9	418.8	-	312.7	482.4	370.3	415	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD155SPK370C4-625AXSP06	360.7	549.2	424.5	474.3	-	359.5	543.5	421.2	469.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD155SPK370C4-632AXSP06	343	527.8	405.6	454.4	-	342.1	522.3	402.6	450.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD155SPK370C5-425AXSP04	284.2	454.8	344	389	-	286.1	452.2	343.4	387.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C5-432AXSP04	261.8	423.9	318.9	361.5	722.5	263.5	421.2	318.9	359.8	714	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C5-525AXSP04	315.8	501.3	381.5	429.6	838.5	317.6	497.9	380.3	427.3	828.2	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK370C5-532AXSP06	313.7	488.1	372.9	418.8	-	312.7	482.4	370.3	415	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD155SPK370C5-625AXSP06	360.7	549.2	424.5	474.3	-	359.5	543.5	421.2	469.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD155SPK370C5-632AXSP06	343	527.8	405.6	454.4	-	342.1	522.3	402.6	450.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD155SPK370C8-425AXSP04	284.2	454.8	344	389	-	286.1	452.2	343.4	387.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C8-432AXSP04	261.8	423.9	318.9	361.5	722.5	263.5	421.2	318.9	359.8	714	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK370C8-525AXSP04	315.8	501.3	381.5	429.6	838.5	317.6	497.9	380.3	427.3	828.2	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK370C8-532AXSP06	313.7	488.1	372.9	418.8	-	312.7	482.4	370.3	415	-	372	28.8	3"	298	19	3"			

EAW-VD1555PK400C3-625AXSP06	360.7	549.2	424.5	474.3	-	359.5	543.5	421.2	469.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400C3-632AXSP06	343	527.8	405.6	454.4	-	342.1	522.3	402.6	450.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400C9-425AXSP04	284.2	454.8	344	389	-	286.1	452.2	343.4	387.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400C9-432AXSP04	261.8	423.9	318.9	361.5	722.5	263.5	421.2	318.9	359.8	714	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400C9-525AXSP04	315.8	501.3	381.5	429.6	838.5	317.6	497.9	380.3	427.3	828.2	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK400C9-532AXSP06	313.7	488.1	372.9	418.8	-	312.7	482.4	370.3	415	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD1555PK400C9-625AXSP06	360.7	549.2	424.5	474.3	-	359.5	543.5	421.2	469.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400C9-632AXSP06	343	527.8	405.6	454.4	-	342.1	522.3	402.6	450.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400K3-425AXSP04	273.3	437.9	331.2	374.2	741	275	435.2	330.5	372.5	731.7	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400K3-432AXSP04	252.2	408.4	307.8	348.7	696	254	406.4	307.1	346.9	686.5	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400K3-525AXSP06	321.4	495.2	380.7	426.1	-	320.6	490.1	377.4	422.1	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD1555PK400K3-532AXSP06	301.9	468.8	359.2	403.2	-	300.9	464	356.1	398.9	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD1555PK400K3-625AXSP06	346.8	526.5	407.3	454.4	-	344.9	520.9	404	449.9	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400K3-632AXSP06	330.2	506.5	390.3	436.4	-	328.6	501.1	386.7	432.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400K9-425AXSP04	273.3	437.9	331.2	374.2	741	275	435.2	330.5	372.5	731.7	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400K9-432AXSP04	252.2	408.4	307.8	348.7	696	254	406.4	307.1	346.9	686.5	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400K9-525AXSP06	321.4	495.2	380.7	426.1	-	320.6	490.1	377.4	422.1	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD1555PK400K9-532AXSP06	301.9	468.8	359.2	403.2	-	300.9	464	356.1	398.9	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD1555PK400K9-625AXSP06	346.8	526.5	407.3	454.4	-	344.9	520.9	404	449.9	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400K9-632AXSP06	330.2	506.5	390.3	436.4	-	328.6	501.1	386.7	432.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK400R3-425AXSP04	278.8	446.4	337.4	381.4	-	280.2	443.2	336.9	379.8	745.7	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400R3-432AXSP04	257.1	415.8	313.6	354.8	709.2	258.8	413.9	313.1	353.8	699.9	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK400R3-525AXSP04	308.3	489.7	373	419.9	819.6	307.4	410.6	373.1	418.2	808.6	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK400R3-532AXSP06	307.4	477.9	365.4	410.2	-	306.6	473.2	363	406.6	-	372	28.8	3"	298	19	3"	446	40.5	3"
EAW-VD1555PK500C3-625AXSP06	352.5	536.2	414.7	462.6	-	350.8	530.1	411	457.7	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK500R3-632AXSP06	335.9	515.5	397.1	444.1	-	334.5	510.3	393.6	439.9	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK500B3-425AXSP04	303.1	485.5	366.7	414.5	-	305.2	483.4	366.1	413.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500B3-432AXSP04	279.6	451.9	340.2	385.3	-	281.4	449.8	340	384.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500B3-525AXSP04	336.1	533.6	405.2	457.5	894.4	338.1	530.9	405.2	455.6	884.7	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500B3-532AXSP04	314.6	505.3	381.8	432.1	853.1	317.1	502.3	381.7	430	843.9	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500B3-625AXSP06	382.6	583.5	450.3	503.5	-	381.6	578	447.8	499.1	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK500B3-632AXSP06	364.7	561.7	431.5	483.1	-	363.8	556	428.4	479.3	-	451	30	3"	361	19.8	3"	541	38.5	4"
EAW-VD1555PK500C2-425AXSP04	318.1	509.5	384.6	435.1	-	319.7	507.2	383.9	433.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C2-432AXSP04	292.3	472.3	355.4	403.1	-	294.2	470	355	401.6	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C2-525AXSP04	355.4	564.1	428.1	483	-	357.3	560.9	427.9	480.8	936.4	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C2-532AXSP04	330.9	531.3	401.2	453.7	899	333.3	528.5	400.8	451.9	888.3	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C2-625AXSP04	381.7	602	459.7	516.4	1000.3	384.3	598.2	459	514.5	987.6	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C2-632AXSP04	359.8	574.1	435.9	492.1	963.5	362.8	571.4	435.5	489.7	950.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C3-425AXSP04	318.1	509.5	384.6	435.1	-	319.7	507.2	383.9	433.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C3-432AXSP04	292.3	472.3	355.4	403.1	-	294.2	470	355	401.6	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C3-525AXSP04	355.4	564.1	428.1	483	-	357.3	560.9	427.9	480.8	936.4	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C3-532AXSP04	330.9	531.3	401.2	453.7	899	333.3	528.5	400.8	451.9	888.3	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C3-625AXSP04	381.7	602	459.7	516.4	1000.3	384.3	598.2	459	514.5	987.6	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C3-632AXSP04	359.8	574.1	435.9	492.1	963.5	362.8	571.4	435.5	489.7	950.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C4-425AXSP04	318.1	509.5	384.6	435.1	-	319.7	507.2	383.9	433.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C4-432AXSP04	292.3	472.3	355.4	403.1	-	294.2	470	355	401.6	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C4-525AXSP04	355.4	564.1	428.1	483	-	357.3	560.9	427.9	480.8	936.4	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C4-532AXSP04	330.9	531.3	401.2	453.7	899	333.3	528.5	400.8	451.9	888.3	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C4-625AXSP04	381.7	602	459.7	516.4	1000.3	384.3	598.2	459	514.5	987.6	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C4-632AXSP04	359.8	574.1	435.9	492.1	963.5	362.8	571.4	435.5	489.7	950.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C5-425AXSP04	318.1	509.5	384.6	435.1	-	319.7	507.2	383.9	433.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C5-432AXSP04	292.3	472.3	355.4	403.1	-	294.2	470	355	401.6	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C5-525AXSP04	355.4	564.1	428.1	483	-	357.3	560.9	427.9	480.8	936.4	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C5-532AXSP04	330.9	531.3	401.2	453.7	899	333.3	528.5	400.8	451.9	888.3	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C5-625AXSP04	381.7	602	459.7	516.4	1000.3	384.3	598.2	459	514.5	987.6	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C5-632AXSP04	359.8	574.1	435.9	492.1	963.5	362.8	571.4	435.5	489.7	950.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C8-425AXSP04	318.1	509.5	384.6	435.1	-	319.7	507.2	383.9	433.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C8-432AXSP04	292.3	472.3	355.4	403.1	-	294.2	470	355	401.6	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C8-525AXSP04	355.4	564.1	428.1	483	-	357.3	560.9	427.9	480.8	936.4	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C8-532AXSP04	330.9	531.3	401.2	453.7	899	333.3	528.5	400.8	451.9	888.3	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD1555PK500C8-625AXSP04	381.7	602	459.7	516.4	1000.3	384.3	598.2	459	514.5	987.6	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C8-632AXSP04	359.8	574.1	435.9	492.1	963.5	362.8	571.4	435.5	489.7	950.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD1555PK500C9-425AXSP04	318.1	509.5	384.6	435.1	-	319.7	507.2	383.9	433.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C9-432AXSP04	292.3	472.3	355.4	403.1	-	294.2	470	355	401.6	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD1555PK500C9-525AXSP04	355.4	564.1																	



EAW-VD155SPK550K9-532AXSP04	316.2	507.1	383.7	433.5	857.7	318.4	504.4	383.2	431.8	847.6	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK550K9-625AXSP04	362.3	570.8	436	490.2	947.3	364.6	567.2	435.2	488.2	935.3	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK550K9-632AXSP06	366.8	565.1	434	486.6	-	365.7	559.8	431.3	481.9	-	451	30	3"	361	19.8	3"	541	26.3	4"
EAW-VD155SPK550R3-425AXSP04	311.8	499.6	377.5	426.9	-	314	497.6	376.9	425.8	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK550R3-432AXSP04	287.5	464.8	349.4	396	-	289.5	462.8	349.2	394.9	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK550R3-525AXSP04	346.8	550.6	418.3	471.7	925.1	349.5	547.8	417.7	469.9	913.8	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK550R3-532AXSP04	323.8	520.3	393.3	444.5	880.9	326.5	517.9	393.1	443.1	869.9	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK550R3-625AXSP04	371.6	585.3	447.3	503.1	972	374.2	581.9	446.7	500.6	960	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK550R3-632AXSP06	375.8	579.6	445.5	498.9	-	374.9	574.5	442.2	494.2	-	451	30	3"	361	19.8	3"	541	26.3	4"
EAW-VD155SPK750C2-425AXSP04	337.7	542.6	409.1	463.4	-	340.3	540.3	409.1	462.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C2-432AXSP04	311.2	503.4	377.8	428.8	-	313.2	500.8	378.1	427.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C2-525AXSP04	377.6	599.5	454.6	513.3	-	379.8	597.2	454.6	511.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C2-532AXSP04	352.3	565	426.2	482.5	-	354.3	562.1	426.5	480.7	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C2-625AXSP04	405	637.6	486.6	547.1	1062.5	408	634.9	486.2	545.4	1051	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C2-632AXSP04	382.4	610.2	463.1	522.4	1024.8	385.8	607.6	462.8	520.8	1012.9	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C3-425AXSP04	337.7	542.6	409.1	463.4	-	340.3	540.3	409.1	462.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C3-432AXSP04	311.2	503.4	377.8	428.8	-	313.2	500.8	378.1	427.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C3-525AXSP04	377.6	599.5	454.6	513.3	-	379.8	597.2	454.6	511.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C3-532AXSP04	352.3	565	426.2	482.5	-	354.3	562.1	426.5	480.7	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C3-632AXSP04	405	637.6	486.6	547.1	1062.5	408	634.9	486.2	545.4	1051	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C3-632AXSP04	382.4	610.2	463.1	522.4	1024.8	385.8	607.6	462.8	520.8	1012.9	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C4-425AXSP04	337.7	542.6	409.1	463.4	-	340.3	540.3	409.1	462.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C4-432AXSP04	311.2	503.4	377.8	428.8	-	313.2	500.8	378.1	427.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C4-525AXSP04	377.6	599.5	454.6	513.3	-	379.8	597.2	454.6	511.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C4-532AXSP04	352.3	565	426.2	482.5	-	354.3	562.1	426.5	480.7	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C4-625AXSP04	405	637.6	486.6	547.1	1062.5	408	634.9	486.2	545.4	1051	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C4-632AXSP04	382.4	610.2	463.1	522.4	1024.8	385.8	607.6	462.8	520.8	1012.9	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C5-425AXSP04	337.7	542.6	409.1	463.4	-	340.3	540.3	409.1	462.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C5-432AXSP04	311.2	503.4	377.8	428.8	-	313.2	500.8	378.1	427.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C5-525AXSP04	377.6	599.5	454.6	513.3	-	379.8	597.2	454.6	511.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C5-532AXSP04	352.3	565	426.2	482.5	-	354.3	562.1	426.5	480.7	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C5-625AXSP04	405	637.6	486.6	547.1	1062.5	408	634.9	486.2	545.4	1051	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C5-632AXSP04	382.4	610.2	463.1	522.4	1024.8	385.8	607.6	462.8	520.8	1012.9	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C8-425AXSP04	337.7	542.6	409.1	463.4	-	340.3	540.3	409.1	462.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C8-432AXSP04	311.2	503.4	377.8	428.8	-	313.2	500.8	378.1	427.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C8-525AXSP04	377.6	599.5	454.6	513.3	-	379.8	597.2	454.6	511.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C8-532AXSP04	352.3	565	426.2	482.5	-	354.3	562.1	426.5	480.7	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C8-625AXSP04	405	637.6	486.6	547.1	1062.5	408	634.9	486.2	545.4	1051	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C8-632AXSP04	382.4	610.2	463.1	522.4	1024.8	385.8	607.6	462.8	520.8	1012.9	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C9-425AXSP04	337.7	542.6	409.1	463.4	-	340.3	540.3	409.1	462.1	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C9-432AXSP04	311.2	503.4	377.8	428.8	-	313.2	500.8	378.1	427.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750C9-532AXSP04	377.6	599.5	454.6	513.3	-	379.8	597.2	454.6	511.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C9-532AXSP04	352.3	565	426.2	482.5	-	354.3	562.1	426.5	480.7	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750C9-625AXSP04	405	637.6	486.6	547.1	1062.5	408	634.9	486.2	545.4	1051	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750C9-632AXSP04	382.4	610.2	463.1	522.4	1024.8	385.8	607.6	462.8	520.8	1012.9	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K2-425AXSP04	326.9	525	395.7	448	-	329.4	522.7	395.8	446.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K2-432AXSP04	301.6	487.1	366.2	415.3	-	303.8	485.4	366.4	414.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K2-525AXSP04	364.3	578.1	439	494.6	-	366.9	575.7	438.8	493.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750K2-532AXSP04	340	546.1	412.6	466.8	925.1	342.7	543.5	412.3	465.1	914.7	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750K2-625AXSP04	390	614.7	469.1	527.9	1023.3	393.1	611.7	469	525.8	1010.4	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K2-632AXSP04	369.1	588.7	446.6	503.6	987.3	371.6	586	447	501.9	975.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K3-425AXSP04	326.9	525	395.7	448	-	329.4	522.7	395.8	446.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K3-432AXSP04	301.6	487.1	366.2	415.3	-	303.8	485.4	366.4	414.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K3-525AXSP04	364.3	578.1	439	494.6	-	366.9	575.7	438.8	493.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750K3-532AXSP04	340	546.1	412.6	466.8	925.1	342.7	543.5	412.3	465.1	914.7	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750K3-625AXSP04	390	614.7	469.1	527.9	1023.3	393.1	611.7	469	525.8	1010.4	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K3-632AXSP04	369.1	588.7	446.6	503.6	987.3	371.6	586	447	501.9	975.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K4-425AXSP04	326.9	525	395.7	448	-	329.4	522.7	395.8	446.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K4-432AXSP04	301.6	487.1	366.2	415.3	-	303.8	485.4	366.4	414.3	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K4-525AXSP04	364.3	578.1	439	494.6	-	366.9	575.7	438.8	493.2	-	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750K4-532AXSP04	340	546.1	412.6	466.8	925.1	342.7	543.5	412.3	465.1	914.7	564	19.4	4"	451	15.4	3"	676	27.3	4"
EAW-VD155SPK750K4-625AXSP04	390	614.7	469.1	527.9	1023.3	393.1	611.7	469	525.8	1010.4	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K4-632AXSP04	369.1	588.7	446.6	503.6	987.3	371.6	586	447	501.9	975.8	676	20.3	4"	541	13.4	4"	812	28.5	4"
EAW-VD155SPK750K5-425AXSP04	326.9	525	395.7	448	-	329.4	522.7	395.8	446.7	-	451	21.3	3"	361	14	3"	541	26.3	4"
EAW-VD155SPK750K5-432AXSP04	301.6	487.1	366.2	415.3	-	303.8	485.4												

EAW-VD155SZB370C5-525AXSP06	364.3	561.5	431.9	483.7	-	363	555.2	427.8	478.1	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370C5-532AXSP06	341.7	531.5	406.3	456.4	-	340.2	525.6	403.1	451.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370C5-625AXSP06	391.9	597.5	461.5	515.3	973.4	389.9	589.8	457.3	509.7	956.6	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370C5-632AXSP06	371.1	572.4	440.4	492.9	941.7	369.6	565.8	436.6	487.7	925.1	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370C8-425AXSP06	326.8	510.6	389.9	438	-	325.8	504.5	386.5	433.9	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370C8-432AXSP06	302	474.9	361.6	407	-	301.1	470.4	358.3	403	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370C8-525AXSP06	364.3	561.5	431.9	483.7	-	363	555.2	427.8	478.1	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370C8-532AXSP06	341.7	531.5	406.3	456.4	-	340.2	525.6	403.1	451.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370C8-625AXSP06	391.9	597.5	461.5	515.3	973.4	389.9	589.8	457.3	509.7	956.6	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370C8-632AXSP06	371.1	572.4	440.4	492.9	941.7	369.6	565.8	436.6	487.7	925.1	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K2-425AXSP06	314.8	491	375.4	421.5	-	313.9	485.9	372.2	417.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K2-432AXSP06	291.5	458.2	348.9	393.1	-	291.2	454	346.3	389.3	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K2-525AXSP06	350.4	539.2	414.7	464.2	-	348.5	532.4	410.6	459.4	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K2-532AXSP06	328.9	510.7	390.9	438.9	-	327.6	505.2	387.9	434.6	834.3	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K2-625AXSP06	375.2	571.5	442.4	493.8	930.5	373.8	564.8	438.3	487.7	914.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K2-632AXSP06	356.5	549.1	422.9	473.2	901.4	355	542.6	419.2	468.1	886.5	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K4-425AXSP06	314.8	491	375.4	421.5	-	313.9	485.9	372.2	417.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K4-432AXSP06	291.5	458.2	348.9	393.1	-	291.2	454	346.3	389.3	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K4-525AXSP06	350.4	539.2	414.7	464.2	-	348.5	532.4	410.6	459.4	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K4-532AXSP06	328.9	510.7	390.9	438.9	-	327.6	505.2	387.9	434.6	834.3	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K4-625AXSP06	375.2	571.5	442.4	493.8	930.5	373.8	564.8	438.3	487.7	914.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K4-632AXSP06	356.5	549.1	422.9	473.2	901.4	355	542.6	419.2	468.1	886.5	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K5-425AXSP06	314.8	491	375.4	421.5	-	313.9	485.9	372.2	417.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K5-432AXSP06	291.5	458.2	348.9	393.1	-	291.2	454	346.3	389.3	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K5-432AXSP06	350.4	539.2	414.7	464.2	-	348.5	532.4	410.6	459.4	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K5-532AXSP06	328.9	510.7	390.9	438.9	-	327.6	505.2	387.9	434.6	834.3	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K5-625AXSP06	375.2	571.5	442.4	493.8	930.5	373.8	564.8	438.3	487.7	914.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K5-632AXSP06	356.5	549.1	422.9	473.2	901.4	355	542.6	419.2	468.1	886.5	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K8-425AXSP06	314.8	491	375.4	421.5	-	313.9	485.9	372.2	417.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K8-432AXSP06	291.5	458.2	348.9	393.1	-	291.2	454	346.3	389.3	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB370K8-525AXSP06	350.4	539.2	414.7	464.2	-	348.5	532.4	410.6	459.4	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K8-532AXSP06	328.9	510.7	390.9	438.9	-	327.6	505.2	387.9	434.6	834.3	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB370K8-625AXSP06	375.2	571.5	442.4	493.8	930.5	373.8	564.8	438.3	487.7	914.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB370K8-632AXSP06	356.5	549.1	422.9	473.2	901.4	355	542.6	419.2	468.1	886.5	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400B3-425AXSP06	319	497.9	379.9	427.3	-	318.2	492.2	377.4	422.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400B3-432AXSP06	295.4	464.7	353.6	398.6	-	294.6	459.8	351.2	394.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400B3-525AXSP06	355	546.7	420.3	470.5	-	353.3	539.9	416.2	465.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400B3-532AXSP06	333.3	517.9	396.2	445	-	332.1	512.4	393.3	440.7	845.4	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400B3-625AXSP06	379.8	578.6	447.8	499.8	942.2	378.2	571.6	443.4	494.1	925.6	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400B3-632AXSP06	361.2	556.6	428.6	479.6	914.1	358.8	550.3	424.9	474.5	899.2	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400C3-425AXSP06	326.8	510.6	389.9	438	-	325.8	504.5	386.5	433.9	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400C3-432AXSP06	302	474.9	361.6	407	-	301.1	470.4	358.3	403	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400C3-525AXSP06	364.3	561.5	431.9	483.7	-	363	555.2	427.8	478.1	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400C3-532AXSP06	341.7	531.5	406.3	456.4	-	340.2	525.6	403.1	451.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400C3-625AXSP06	391.9	597.5	461.5	515.3	973.4	389.9	589.8	457.3	509.7	956.6	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400C3-632AXSP06	371.1	572.4	440.4	492.9	941.7	369.6	565.8	436.6	487.7	925.1	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400C9-425AXSP06	326.8	510.6	389.9	438	-	325.8	504.5	386.5	433.9	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400C9-432AXSP06	302	474.9	361.6	407	-	301.1	470.4	358.3	403	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400C9-525AXSP06	364.3	561.5	431.9	483.7	-	363	555.2	427.8	478.1	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400C9-532AXSP06	341.7	531.5	406.3	456.4	-	340.2	525.6	403.1	451.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400C9-625AXSP06	391.9	597.5	461.5	515.3	973.4	389.9	589.8	457.3	509.7	956.6	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400C9-632AXSP06	371.1	572.4	440.4	492.9	941.7	369.6	565.8	436.6	487.7	925.1	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400K3-425AXSP06	314.8	491	375.4	421.5	-	313.9	485.9	372.2	417.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400K3-432AXSP06	291.5	458.2	348.9	393.1	-	291.2	454	346.3	389.3	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400K3-525AXSP06	350.4	539.2	414.7	464.2	-	348.5	532.4	410.6	459.4	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400K3-532AXSP06	328.9	510.7	390.9	438.9	-	327.6	505.2	387.9	434.6	834.3	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400K3-625AXSP06	375.2	571.5	442.4	493.8	930.5	373.8	564.8	438.3	487.7	914.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400K3-632AXSP06	356.5	549.1	422.9	473.2	901.4	355	542.6	419.2	468.1	886.5	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400K9-425AXSP06	314.8	491	375.4	421.5	-	313.9	485.9	372.2	417.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400K9-432AXSP06	291.5	458.2	348.9	393.1	-	291.2	454	346.3	389.3	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB400K9-525AXSP06	350.4	539.2	414.7	464.2	-	348.5	532.4	410.6	459.4	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400K9-532AXSP06	328.9	510.7	390.9	438.9	-	327.6	505.2	387.9	434.6	834.3	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB400K9-625AXSP06	375.2	571.5	442.4	493.8	930.5	373.8	564.8	438.3	487.7	914.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400K9-632AXSP06	356.5	549.1	422.9	473.2	901.4	355	542.6	419.2	468.1	886.5	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB400R3-425AXSP06	363.8	5																	

EAW-VD155SZB550C8-432AXSP06	337	532.2	403.9	455.6	-	336.1	526.9	401.5	451.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550C8-525AXSP06	410.4	635.8	487.3	546.5	-	408.8	628.4	483	540.6	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550C8-532AXSP06	383.1	597.6	456.2	513.4	-	382	591.6	453.3	508	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550C8-625AXSP06	443.4	678.8	523.4	585.1	-	441.7	670.6	518.4	578.4	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550C8-632AXSP06	419	647.5	496.4	556.4	-	417.2	639.8	492.7	551	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550C9-425AXSP04	340.2	552.2	416.2	471.8	939.9	343	549.2	415.8	469.2	928.3	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB550C9-432AXSP06	337	532.2	403.9	455.6	-	336.1	526.9	401.5	451.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550C9-525AXSP06	410.4	635.8	487.3	546.5	-	408.8	628.4	483	540.6	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550C9-532AXSP06	383.1	597.6	456.2	513.4	-	382	591.6	453.3	508	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550C9-625AXSP06	443.4	678.8	523.4	585.1	-	441.7	670.6	518.4	578.4	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550C9-632AXSP06	419	647.5	496.4	556.4	-	417.2	639.8	492.7	551	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K2-425AXSP06	350.9	549.7	419.1	471.4	-	350.5	544.8	416.2	467.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K2-432AXSP06	324.3	511.5	388.9	438.3	-	323.9	506.6	386	434.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K2-525AXSP06	391.8	605.8	465	521.2	-	390.4	599.7	461	515.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K2-532AXSP06	366.8	571.9	437.3	491	-	365.9	566.4	433.9	486.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K2-625AXSP06	421.9	644.9	497.8	556.2	-	420.4	637.2	493.2	550	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K2-632AXSP06	400.2	617.2	473.9	530.8	-	398.5	609.9	470.3	525.8	1001.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K3-425AXSP06	350.9	549.7	419.1	471.4	-	350.5	544.8	416.2	467.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K3-432AXSP06	324.3	511.5	388.9	438.3	-	323.9	506.6	386	434.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K3-525AXSP06	391.8	605.8	465	521.2	-	390.4	599.7	461	515.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K3-532AXSP06	366.8	571.9	437.3	491	-	365.9	566.4	433.9	486.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K3-625AXSP06	421.9	644.9	497.8	556.2	-	420.4	637.2	493.2	550	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K3-632AXSP06	400.2	617.2	473.9	530.8	-	398.5	609.9	470.3	525.8	1001.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K5-425AXSP06	350.9	549.7	419.1	471.4	-	350.5	544.8	416.2	467.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K5-432AXSP06	324.3	511.5	388.9	438.3	-	323.9	506.6	386	434.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K5-525AXSP06	391.8	605.8	465	521.2	-	390.4	599.7	461	515.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K5-532AXSP06	366.8	571.9	437.3	491	-	365.9	566.4	433.9	486.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K5-625AXSP06	421.9	644.9	497.8	556.2	-	420.4	637.2	493.2	550	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K5-632AXSP06	400.2	617.2	473.9	530.8	-	398.5	609.9	470.3	525.8	1001.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K8-425AXSP06	350.9	549.7	419.1	471.4	-	350.5	544.8	416.2	467.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K8-432AXSP06	324.3	511.5	388.9	438.3	-	323.9	506.6	386	434.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K8-525AXSP06	391.8	605.8	465	521.2	-	390.4	599.7	461	515.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K8-532AXSP06	366.8	571.9	437.3	491	-	365.9	566.4	433.9	486.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K8-625AXSP06	421.9	644.9	497.8	556.2	-	420.4	637.2	493.2	550	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K8-632AXSP06	400.2	617.2	473.9	530.8	-	398.5	609.9	470.3	525.8	1001.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K9-425AXSP06	350.9	549.7	419.1	471.4	-	350.5	544.8	416.2	467.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K9-432AXSP06	324.3	511.5	388.9	438.3	-	323.9	506.6	386	434.6	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550K9-525AXSP06	391.8	605.8	465	521.2	-	390.4	599.7	461	515.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K9-532AXSP06	366.8	571.9	437.3	491	-	365.9	566.4	433.9	486.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550K9-625AXSP06	421.9	644.9	497.8	556.2	-	420.4	637.2	493.2	550	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K9-632AXSP06	400.2	617.2	473.9	530.8	-	398.5	609.9	470.3	525.8	1001.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K9-625AXSP06	421.9	644.9	497.8	556.2	-	420.4	637.2	493.2	550	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550K9-632AXSP06	400.2	617.2	473.9	530.8	-	398.5	609.9	470.3	525.8	1001.4	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550R3-425AXSP04	334.8	543.7	409.4	464	924.9	337.7	541.2	409.4	462.6	914.4	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB550R3-432AXSP06	333.2	525.4	399	449.9	-	332.3	520.6	396.9	446.4	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB550R3-525AXSP06	402.8	622.7	477.5	535.4	-	401.5	616.6	474.3	530.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550R3-532AXSP06	377	588.5	448.9	505	-	375.7	582.2	445.6	500.2	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB550R3-625AXSP06	433.5	663.1	511.5	571.7	-	432.3	655.8	507.3	565.9	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB550R3-632AXSP06	410.7	634.2	487.2	545.9	-	409.8	627.8	483.1	541	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750C2-425AXSP04	365.1	592	445.5	505.8	1011.1	368.6	589.9	446	503.9	998.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750C2-432AXSP04	334.6	549	411.8	467.7	942.1	338.1	546.8	411.7	466.6	932.5	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750C2-525AXSP06	438.7	681.9	521.3	585.3	-	437.9	675	518.5	580.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750C2-532AXSP06	409.9	641.9	488.7	550.5	-	408.9	635.5	485.6	545.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750C2-625AXSP06	473.4	726.6	559.9	626.3	-	472.5	719.8	555.6	620.3	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750C2-632AXSP06	447.6	693.9	531.6	596.3	-	446.6	686.7	528.5	591.5	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750C3-425AXSP04	365.1	592	445.5	505.8	1011.1	368.6	589.9	446	503.9	998.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750C3-432AXSP04	334.6	549	411.8	467.7	942.1	338.1	546.8	411.7	466.6	932.5	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750C3-525AXSP06	438.7	681.9	521.3	585.3	-	437.9	675	518.5	580.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750C3-532AXSP06	409.9	641.9	488.7	550.5	-	408.9	635.5	485.6	545.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750C3-625AXSP06	473.4	726.6	559.9	626.3	-	472.5	719.8	555.6	620.3	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750C3-632AXSP06	447.6	693.9	531.6	596.3	-	446.6	686.7	528.5	591.5	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750C4-425AXSP04	365.1	592	445.5	505.8	1011.1	368.6	589.9	446	503.9	998.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750C4-432AXSP04	334.6	549	411.8	467.7	942.1	338.1	546.8	411.7	466.6	932.5	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750C4-525AXSP06	438.7	681.9	521.3	585.3	-	437.9	675	518.5	580.8	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750C4-532AXSP06	409.9	641.9	488.7	550.5	-	408.9	635.5	485.6	545.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZ																			

EAW-VD155SZB750K4-425AXSP04	352.6	572.9	431	489	976.7	356.2	570.7	431.4	487.1	964.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750K4-432AXSP06	349.8	553.3	419.9	474	-	349.8	548.7	417.4	469.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB750K4-525AXSP06	423.9	656.9	503.6	565	-	422.9	651	499.9	559.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K4-532AXSP06	396.3	619.5	473.1	531.7	-	395.3	614.3	470	527	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K4-625AXSP06	456.4	699.4	538.8	602.5	-	455.7	692.4	534.9	597.7	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K4-632AXSP06	432.7	669.6	513.6	575.9	-	431.5	662.5	509.6	570.2	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K5-425AXSP04	352.6	572.9	431	489	976.7	356.2	570.7	431.4	487.1	964.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750K5-432AXSP06	349.8	553.3	419.9	474	-	349.8	548.7	417.4	469.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB750K5-525AXSP06	423.9	656.9	503.6	565	-	422.9	651	499.9	559.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K5-532AXSP06	396.3	619.5	473.1	531.7	-	395.3	614.3	470	527	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K5-625AXSP06	456.4	699.4	538.8	602.5	-	455.7	692.4	534.9	597.7	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K5-632AXSP06	432.7	669.6	513.6	575.9	-	431.5	662.5	509.6	570.2	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K8-425AXSP04	352.6	572.9	431	489	976.7	356.2	570.7	431.4	487.1	964.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750K8-432AXSP06	349.8	553.3	419.9	474	-	349.8	548.7	417.4	469.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB750K8-525AXSP06	423.9	656.9	503.6	565	-	422.9	651	499.9	559.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K8-532AXSP06	396.3	619.5	473.1	531.7	-	395.3	614.3	470	527	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K8-625AXSP06	456.4	699.4	538.8	602.5	-	455.7	692.4	534.9	597.7	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K8-632AXSP06	432.7	669.6	513.6	575.9	-	431.5	662.5	509.6	570.2	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K9-425AXSP04	352.6	572.9	431	489	976.7	356.2	570.7	431.4	487.1	964.8	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750K9-432AXSP06	349.8	553.3	419.9	474	-	349.8	548.7	417.4	469.8	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB750K9-525AXSP06	423.9	656.9	503.6	565	-	422.9	651	499.9	559.7	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K9-532AXSP06	396.3	619.5	473.1	531.7	-	395.3	614.3	470	527	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750K9-625AXSP06	456.4	699.4	538.8	602.5	-	455.7	692.4	534.9	597.7	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750K9-632AXSP06	432.7	669.6	513.6	575.9	-	431.5	662.5	509.6	570.2	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750R3-425AXSP04	345.5	660.3	422	478.6	954.5	348.9	558.2	422.3	477.5	944.2	609	18.2	4"	487	15.1	3"	730	25.5	4"
EAW-VD155SZB750R3-432AXSP06	343	541.8	411.6	464.4	-	342.9	537.3	409	460.2	-	406	27	3"	325	17.8	3"	487	37.9	3"
EAW-VD155SZB750R3-525AXSP06	414.3	642.3	492	551.9	-	413.3	636.5	489.1	547.5	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750R3-532AXSP06	387.9	606.6	462.9	520.1	-	387.5	600.5	459.8	516.3	-	507	28.8	3"	406	19	3"	609	35.6	4"
EAW-VD155SZB750R3-625AXSP06	445.4	682.1	525.8	588.6	-	444.6	675.9	522.5	583	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZB750R3-632AXSP06	423	654	501.9	562.6	-	422.3	647.8	498	557.1	-	609	26.1	4"	487	20.4	3"	730	36.7	4"
EAW-VD155SZK01767-425AXSP04	464.6	747	562.6	637.5	-	466.4	742.5	561.8	634.7	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK01767-432AXSP06	424.4	686.4	515.4	585	-	426.3	682.2	514.8	582.4	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK01767-525AXSP04	524.6	833.9	632.1	714.3	-	526.7	828.7	630.7	709.7	-	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD155SZK01767-532AXSP04	484	776.9	586	663.9	-	486.2	771.6	584.6	660.3	-	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD155SZK01767-625AXSP04	574.5	905.4	689.8	777.2	1512.8	577.1	898.6	687.1	772.3	1489.4	913	18.8	(2) 4"	730	14.9	4"	1096	26.4	(2) 4"
EAW-VD155SZK01767-632AXSP04	535.1	852.9	647.3	730.7	1436.4	537.8	847.2	645.5	726.7	1416	913	18.8	(2) 4"	730	14.9	4"	1096	26.4	(2) 4"
EAW-VD155SZK370C2-425AXSP06	345.4	535.8	410.3	460.4	-	343.3	528.8	405.6	454.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C2-432AXSP06	319.2	498.7	380.4	428.3	-	317.8	492.6	377.1	423.5	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C2-525AXSP06	385.2	589.3	454.4	508.4	-	382.5	581.8	449.2	501.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C2-532AXSP06	361	556.8	427.4	479.6	-	358.4	550	422.9	473.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C2-625AXSP06	414.5	626.4	485.9	541.5	1015.6	411.4	617.6	480.3	534.3	997.1	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C2-632AXSP06	392.9	600.7	463.3	518.1	981.8	390.1	592.1	457.9	511.1	964.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C4-425AXSP06	345.4	535.8	410.3	460.4	-	343.3	528.8	405.6	454.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C4-432AXSP06	319.2	498.7	380.4	428.3	-	317.8	492.6	377.1	423.5	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C4-525AXSP06	385.2	589.3	454.4	508.4	-	382.5	581.8	449.2	501.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C4-532AXSP06	361	556.8	427.4	479.6	-	358.4	550	422.9	473.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C4-625AXSP06	414.5	626.4	485.9	541.5	1015.6	411.4	617.6	480.3	534.3	997.1	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C4-632AXSP06	392.9	600.7	463.3	518.1	981.8	390.1	592.1	457.9	511.1	964.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C5-425AXSP06	345.4	535.8	410.3	460.4	-	343.3	528.8	405.6	454.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C5-432AXSP06	319.2	498.7	380.4	428.3	-	317.8	492.6	377.1	423.5	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C5-525AXSP06	385.2	589.3	454.4	508.4	-	382.5	581.8	449.2	501.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C5-532AXSP06	361	556.8	427.4	479.6	-	358.4	550	422.9	473.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C5-625AXSP06	414.5	626.4	485.9	541.5	1015.6	411.4	617.6	480.3	534.3	997.1	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C5-632AXSP06	392.9	600.7	463.3	518.1	981.8	390.1	592.1	457.9	511.1	964.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C8-425AXSP06	345.4	535.8	410.3	460.4	-	343.3	528.8	405.6	454.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C8-432AXSP06	319.2	498.7	380.4	428.3	-	317.8	492.6	377.1	423.5	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370C8-525AXSP06	385.2	589.3	454.4	508.4	-	382.5	581.8	449.2	501.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C8-532AXSP06	361	556.8	427.4	479.6	-	358.4	550	422.9	473.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370C8-625AXSP06	414.5	626.4	485.9	541.5	1015.6	411.4	617.6	480.3	534.3	997.1	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370C8-632AXSP06	392.9	600.7	463.3	518.1	981.8	390.1	592.1	457.9	511.1	964.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK370K2-425AXSP06	332.7	515.9	395	443	-	331.2	509.3	391.2	438.4	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370K2-432AXSP06	308.5	481.8	368	413.4	-	307	475.8	364.1	408.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK370K2-525AXSP06	370	565.3	436.3	487.3	-	367.6	558.3	431.5	481.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370K2-532AXSP06	347.5	535.9	411.9	461.3	-	345.5	529.5	407.6	455.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK370K2-625AXSP06	396.9	599.9	465.2	518.3	971	394.4	591.5	460.4	511.4</										

EAW-VD155SZK400C9-632AXSP06	392.9	600.7	463.3	518.1	981.8	390.1	592.1	457.9	511.1	964.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK400K3-425AXSP06	332.7	515.9	395	443	-	331.2	509.3	391.2	438.4	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK400K3-632AXSP06	308.5	481.8	368	413.4	-	307	475.8	364.1	408.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK400K3-525AXSP06	370	565.3	436.3	487.3	-	367.6	558.3	431.5	481.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK400K3-532AXSP06	347.5	535.9	411.9	461.3	-	345.5	529.5	407.6	455.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK400K3-625AXSP06	396.9	599.9	465.2	518.3	971	394.4	591.5	460.4	511.4	952.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK400K3-632AXSP06	377	576.4	445	496.8	941.3	374.9	568.4	439.9	490.9	923.9	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK400K9-425AXSP06	332.7	515.9	395	443	-	331.2	509.3	391.2	438.4	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK400K9-432AXSP06	308.5	481.8	368	413.4	-	307	475.8	364.1	408.8	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK400K9-525AXSP06	370	565.3	436.3	487.3	-	367.6	558.3	431.5	481.7	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK400K9-532AXSP06	347.5	535.9	411.9	461.3	-	345.5	529.5	407.6	455.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK400K9-625AXSP06	396.9	599.9	465.2	518.3	971	394.4	591.5	460.4	511.4	952.3	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK400K9-632AXSP06	377	576.4	445	496.8	941.3	374.9	568.4	439.9	490.9	923.9	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK400R3-425AXSP06	339.7	526.6	403.4	452.6	-	337.8	520.8	399.7	447.4	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK400R3-432AXSP06	315	492.6	375.3	422.5	-	313.8	486.8	372.3	418	-	406	29.5	3"	325	19.4	3"	487	41.4	3"
EAW-VD155SZK400R3-525AXSP06	377.6	578.2	445.4	498.3	-	375.3	570.5	440.7	492.1	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK400R3-532AXSP06	354.8	547.7	420.7	471.2	-	353	541.3	416.5	465.6	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK400R3-625AXSP06	405.4	613.1	475.3	529.5	992.6	403	604	469.9	522.7	973.8	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK400R3-632AXSP06	385.4	588.8	454.3	507.9	962	382.8	580.8	449.3	501.4	945.5	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK500B3-425AXSP04	348.1	557.6	422.8	477.2	942.8	350	553.9	421	474	929.2	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK500B3-432AXSP04	320.4	519	391.6	443.1	882.1	322.1	515.4	389.9	440.7	869.8	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK500B3-525AXSP06	414.5	635.9	489.3	547.9	-	411.8	628	484.6	541.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK500B3-532AXSP06	388.3	600.9	460.9	516.8	-	386.1	593.5	456.6	511	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK500B3-625AXSP06	445.7	675.8	523.4	583.6	-	443	667.2	518.1	576.7	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK500B3-632AXSP06	422.8	648.1	499.5	558.2	-	420.4	639.8	494.5	551.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C2-425AXSP04	363.8	583.3	441.5	498.8	986.5	365.9	578.4	439.5	495.2	971.9	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C2-432AXSP04	333.9	540.4	407.7	461.7	920.1	335.5	536.3	406.4	458.9	906.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C3-525AXSP06	434.1	668.2	513.4	575.3	-	431.7	659.4	508.1	568.2	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C2-532AXSP06	405.3	628.5	481.3	540.1	-	402.9	620.6	476.8	533.8	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C2-625AXSP06	469.5	713.8	551.5	616	-	466.4	704.3	546.3	608.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C2-632AXSP06	443.3	679.9	524	585.9	-	440.6	671.6	518.4	579.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C3-425AXSP04	363.8	583.3	441.5	498.8	986.5	365.9	578.4	439.5	495.2	971.9	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C3-432AXSP04	333.9	540.4	407.7	461.7	920.1	335.5	536.3	406.4	458.9	906.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C3-525AXSP06	434.1	668.2	513.4	575.3	-	431.7	659.4	508.1	568.2	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C3-625AXSP06	405.3	628.5	481.3	540.1	-	402.9	620.6	476.8	533.8	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C3-632AXSP06	469.5	713.8	551.5	616	-	466.4	704.3	546.3	608.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C3-632AXSP06	443.3	679.9	524	585.9	-	440.6	671.6	518.4	579.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C4-425AXSP04	363.8	583.3	441.5	498.8	986.5	365.9	578.4	439.5	495.2	971.9	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C4-432AXSP04	333.9	540.4	407.7	461.7	920.1	335.5	536.3	406.4	458.9	906.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C4-525AXSP06	434.1	668.2	513.4	575.3	-	431.7	659.4	508.1	568.2	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C4-532AXSP06	405.3	628.5	481.3	540.1	-	402.9	620.6	476.8	533.8	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C4-625AXSP06	469.5	713.8	551.5	616	-	466.4	704.3	546.3	608.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C4-632AXSP06	443.3	679.9	524	585.9	-	440.6	671.6	518.4	579.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C5-425AXSP04	363.8	583.3	441.5	498.8	986.5	365.9	578.4	439.5	495.2	971.9	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C5-432AXSP04	333.9	540.4	407.7	461.7	920.1	335.5	536.3	406.4	458.9	906.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C5-525AXSP06	434.1	668.2	513.4	575.3	-	431.7	659.4	508.1	568.2	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C5-625AXSP06	405.3	628.5	481.3	540.1	-	402.9	620.6	476.8	533.8	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C5-625AXSP06	469.5	713.8	551.5	616	-	466.4	704.3	546.3	608.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C5-632AXSP06	443.3	679.9	524	585.9	-	440.6	671.6	518.4	579.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C8-425AXSP04	363.8	583.3	441.5	498.8	986.5	365.9	578.4	439.5	495.2	971.9	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C8-432AXSP04	333.9	540.4	407.7	461.7	920.1	335.5	536.3	406.4	458.9	906.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C8-525AXSP06	434.1	668.2	513.4	575.3	-	431.7	659.4	508.1	568.2	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C8-532AXSP06	405.3	628.5	481.3	540.1	-	402.9	620.6	476.8	533.8	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C8-625AXSP06	469.5	713.8	551.5	616	-	466.4	704.3	546.3	608.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C8-632AXSP06	443.3	679.9	524	585.9	-	440.6	671.6	518.4	579.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C9-425AXSP04	363.8	583.3	441.5	498.8	986.5	365.9	578.4	439.5	495.2	971.9	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C9-432AXSP04	333.9	540.4	407.7	461.7	920.1	335.5	536.3	406.4	458.9	906.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550C9-525AXSP06	434.1	668.2	513.4	575.3	-	431.7	659.4	508.1	568.2	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C9-632AXSP06	405.3	628.5	481.3	540.1	-	402.9	620.6	476.8	533.8	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550C9-625AXSP06	469.5	713.8	551.5	616	-	466.4	704.3	546.3	608.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550C9-632AXSP06	443.3	679.9	524	585.9	-	440.6	671.6	518.4	579.3	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD155SZK550K2-425AXSP06	349.3	559.6	423.5	478.2	944.8	350.8	555.1	421.8	475.7	931.3	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550K2-432AXSP04	321.4	520.2	392.4	444.9	885.6	323.4	516.7	391.5	441.7	873.4	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD155SZK550K2-525AXSP06	415.3	638	490.9	549	-	413.1	630	486.1	542.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD155SZK550K2-532AXSP06	389																		

EAW-VD1555ZK550R3-625AXSP06	459.7	698.7	540.7	603.1	-	457.6	689.8	535.2	595.9	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK550R3-632AXSP06	435.9	669	515.2	575.9	-	433.7	660.6	510.1	569.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C2-425AXSP04	392.4	627.7	474.3	536.6	-	393.9	623.3	472.3	533.5	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C2-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C2-525AXSP04	436.1	693.7	527.2	594.1	1161.8	438.7	687.9	525.6	590.7	1145.5	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750C2-532AXSP06	435.5	676.9	517.7	581.6	-	433.6	670.1	513.5	575.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750C2-625AXSP06	503.6	768.5	593.5	662.5	-	501.2	758.6	588.1	655.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C2-632AXSP06	476.4	732.7	563.5	630.5	-	473.6	723.9	558.4	623.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C3-425AXSP04	392.4	627.7	474.3	536.6	-	393.9	623.3	472.9	533.5	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C3-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C3-525AXSP04	436.1	693.7	527.2	594.1	1161.8	438.7	687.9	525.6	590.7	1145.5	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750C3-532AXSP06	435.5	676.9	517.7	581.6	-	433.6	670.1	513.5	575.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750C3-625AXSP06	503.6	768.5	593.5	662.5	-	501.2	758.6	588.1	655.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C3-632AXSP06	476.4	732.7	563.5	630.5	-	473.6	723.9	558.4	623.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C4-425AXSP04	392.4	627.7	474.3	536.6	-	393.9	623.3	472.9	533.5	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C4-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C4-525AXSP04	436.1	693.7	527.2	594.1	1161.8	438.7	687.9	525.6	590.7	1145.5	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750C4-532AXSP06	435.5	676.9	517.7	581.6	-	433.6	670.1	513.5	575.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750C4-625AXSP06	503.6	768.5	593.5	662.5	-	501.2	758.6	588.1	655.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C4-632AXSP06	476.4	732.7	563.5	630.5	-	473.6	723.9	558.4	623.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C5-425AXSP04	392.4	627.7	474.3	536.6	-	393.9	623.3	472.9	533.5	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C5-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C5-525AXSP04	436.1	693.7	527.2	594.1	1161.8	438.7	687.9	525.6	590.7	1145.5	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750C5-532AXSP06	435.5	676.9	517.7	581.6	-	433.6	670.1	513.5	575.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750C5-625AXSP06	503.6	768.5	593.5	662.5	-	501.2	758.6	588.1	655.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C5-632AXSP06	476.4	732.7	563.5	630.5	-	473.6	723.9	558.4	623.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C8-432AXSP04	392.4	627.7	474.3	536.6	-	393.9	623.3	472.9	533.5	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C8-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C8-525AXSP04	436.1	693.7	527.2	594.1	1161.8	438.7	687.9	525.6	590.7	1145.5	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750C8-525AXSP04	435.5	676.9	517.7	581.6	-	433.6	670.1	513.5	575.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750C8-625AXSP06	503.6	768.5	593.5	662.5	-	501.2	758.6	588.1	655.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C8-625AXSP06	476.4	732.7	563.5	630.5	-	473.6	723.9	558.4	623.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C8-632AXSP06	392.4	627.7	474.3	536.6	-	393.9	623.3	472.9	533.5	-	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C9-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C9-432AXSP04	359.6	581.4	438	496.5	991.9	361.6	578.1	437.3	493.5	979	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750C9-525AXSP04	436.1	693.7	527.2	594.1	1161.8	438.7	687.9	525.6	590.7	1145.5	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750C9-532AXSP06	435.5	676.9	517.7	581.6	-	433.6	670.1	513.5	575.5	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750C9-625AXSP06	503.6	768.5	593.5	662.5	-	501.2	758.6	588.1	655.2	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750C9-632AXSP06	476.4	732.7	563.5	630.5	-	473.6	723.9	558.4	623.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K2-425AXSP04	379.4	606.9	459.2	519.2	-	380.9	603.7	458	516.3	1014.4	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K2-432AXSP04	348.7	564.1	425.4	481.3	962.4	350.7	561	424.2	479.4	948.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K2-525AXSP04	421.1	668.6	508.8	573	1118.5	422.9	664	507.1	569.8	1103	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750K2-525AXSP04	421.2	654.6	501.3	562.9	-	419.5	647.3	496.6	556.3	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750K2-625AXSP06	485.7	739.4	571.5	637.7	-	483.2	730.5	566.1	630.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K2-625AXSP06	459.7	707	543.5	608.9	-	457.7	698.6	538.6	602.1	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K3-425AXSP04	379.4	606.9	459.2	519.2	-	380.9	603.7	458	516.3	1014.4	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K3-432AXSP04	348.7	564.1	425.4	481.3	962.4	350.7	561	424.2	479.4	948.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K3-525AXSP04	421.1	668.6	508.8	573	1118.5	422.9	664	507.1	569.8	1103	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750K3-532AXSP06	421.2	654.6	501.3	562.9	-	419.5	647.3	496.6	556.3	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750K3-625AXSP06	485.7	739.4	571.5	637.7	-	483.2	730.5	566.1	630.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K3-632AXSP06	459.7	707	543.5	608.9	-	457.7	698.6	538.6	602.1	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K4-425AXSP04	379.4	606.9	459.2	519.2	-	380.9	603.7	458	516.3	1014.4	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K4-432AXSP04	348.7	564.1	425.4	481.3	962.4	350.7	561	424.2	479.4	948.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K4-525AXSP04	421.1	668.6	508.8	573	1118.5	422.9	664	507.1	569.8	1103	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750K4-525AXSP04	421.2	654.6	501.3	562.9	-	419.5	647.3	496.6	556.3	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750K4-625AXSP06	485.7	739.4	571.5	637.7	-	483.2	730.5	566.1	630.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K4-632AXSP06	459.7	707	543.5	608.9	-	457.7	698.6	538.6	602.1	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K5-425AXSP04	379.4	606.9	459.2	519.2	-	380.9	603.7	458	516.3	1014.4	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K5-432AXSP04	348.7	564.1	425.4	481.3	962.4	350.7	561	424.2	479.4	948.7	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K5-432AXSP04	421.1	668.6	508.8	573	1118.5	422.9	664	507.1	569.8	1103	755	21.1	4"	604	13.9	4"	906	25.8	(2) 4"
EAW-VD1555ZK750K5-532AXSP06	421.2	654.6	501.3	562.9	-	419.5	647.3	496.6	556.3	-	507	31.2	3"	406	20.6	3"	609	39.1	4"
EAW-VD1555ZK750K5-625AXSP06	485.7	739.4	571.5	637.7	-	483.2	730.5	566.1	630.5	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K5-632AXSP06	459.7	707	543.5	608.9	-	457.7	698.6	538.6	602.1	-	609	28.6	4"	487	22	3"	730	40.1	4"
EAW-VD1555ZK750K8-425AXSP04	379.4	606.9	459.2	519.2	-	380.9	603.7	458	516.3	1014.4	609	19.8	4"	487	16.2	3"	730	27.8	4"
EAW-VD1555ZK750K8-432AXSP04	348.7	564.1	425.4																

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1556PB370C8-532AXSP04	341.6	542.7	412	465.1	915.4	342.8	540.1	410.9	462.7	904	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370C8-625AXSP04	389.2	607.6	465.9	522.8	1004.9	391.3	604.3	464.8	519.8	991.9	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370C8-632AXSP04	369.8	584.3	445.8	501.1	974.2	371.5	580.8	444	498.6	961.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K2-425AXSP04	316.1	503	380.5	430.2	-	317.4	499.8	379.6	428.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K2-432AXSP04	292.5	468.8	354	400.6	-	293.7	466.3	352.9	398.2	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K2-525AXSP04	350.7	551.2	420.2	473.2	920.6	351.8	547.9	419.2	470.9	908.9	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K2-532AXSP04	328.6	522.7	396.7	447.7	879.1	330.2	519.9	395.5	445.1	869	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K2-625AXSP04	374.5	584.6	448.2	502.7	964.8	376.1	580.7	446.5	499.8	951.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K2-632AXSP04	355.4	561.4	428.2	481.8	934.9	357.4	557.8	426.9	479.3	922.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K4-425AXSP04	316.1	503	380.5	430.2	-	317.4	499.8	379.6	428.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K4-432AXSP04	292.5	468.8	354	400.6	-	293.7	466.3	352.9	398.2	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K4-525AXSP04	350.7	551.2	420.2	473.2	920.6	351.8	547.9	419.2	470.9	908.9	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K4-532AXSP04	328.6	522.7	396.7	447.7	879.1	330.2	519.9	395.5	445.1	869	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K4-625AXSP04	374.5	584.6	448.2	502.7	964.8	376.1	580.7	446.5	499.8	951.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K4-632AXSP04	355.4	561.4	428.2	481.8	934.9	357.4	557.8	426.9	479.3	922.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K5-425AXSP04	316.1	503	380.5	430.2	-	317.4	499.8	379.6	428.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K5-432AXSP04	292.5	468.8	354	400.6	-	293.7	466.3	352.9	398.2	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K5-525AXSP04	350.7	551.2	420.2	473.2	920.6	351.8	547.9	419.2	470.9	908.9	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K5-532AXSP04	328.6	522.7	396.7	447.7	879.1	330.2	519.9	395.5	445.1	869	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K5-625AXSP04	374.5	584.6	448.2	502.7	964.8	376.1	580.7	446.5	499.8	951.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K5-632AXSP04	355.4	561.4	428.2	481.8	934.9	357.4	557.8	426.9	479.3	922.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K8-425AXSP04	316.1	503	380.5	430.2	-	317.4	499.8	379.6	428.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K8-432AXSP04	292.5	468.8	354	400.6	-	293.7	466.3	352.9	398.2	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB370K8-525AXSP04	350.7	551.2	420.2	473.2	920.6	351.8	547.9	419.2	470.9	908.9	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K8-532AXSP04	328.6	522.7	396.7	447.7	879.1	330.2	519.9	395.5	445.1	869	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB370K8-625AXSP04	374.5	584.6	448.2	502.7	964.8	376.1	580.7	446.5	499.8	951.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB370K8-632AXSP04	355.4	561.4	428.2	481.8	934.9	357.4	557.8	426.9	479.3	922.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400B3-425AXSP04	319.1	507.2	384.1	433.6	-	320.6	504.3	383.5	431.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400B3-432AXSP04	295.5	473.7	357.4	404.5	-	297.1	471.5	356.7	403.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400B3-525AXSP04	352.6	555.1	423.2	475.8	926.2	354.6	551.7	421.9	474	915.4	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400B3-532AXSP04	331.6	527.7	400.4	451.8	887.7	333.3	524.3	399.3	449.5	876.7	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400B3-625AXSP04	375	585.4	449.4	504.1	966.3	377.3	582.7	448	501.5	954.8	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400B3-632AXSP04	357.8	565.3	431.1	485.1	941.5	359.7	561.5	429.7	483.1	930.2	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400C3-425AXSP04	328	522.3	395.1	446.2	-	329.6	519.4	394.4	444.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400C3-432AXSP04	303.1	485.8	366.6	415.3	-	304.5	483.3	365.8	413	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400C3-525AXSP04	364.5	574	437	492.3	-	366.4	569.9	436.1	489.4	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400C3-532AXSP04	341.6	542.7	412	465.1	915.4	342.8	540.1	410.9	462.7	904	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400C3-625AXSP04	389.2	607.6	465.9	522.8	1004.9	391.3	604.3	464.8	519.8	991.9	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400C3-632AXSP04	369.8	584.3	445.8	501.1	974.2	371.5	580.8	444	498.6	961.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400C9-425AXSP04	328	522.3	395.1	446.2	-	329.6	519.4	394.4	444.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400C9-432AXSP04	303.1	485.8	366.6	415.3	-	304.5	483.3	365.8	413	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400C9-525AXSP04	364.5	574	437	492.3	-	366.4	569.9	436.1	489.4	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400C9-532AXSP04	341.6	542.7	412	465.1	915.4	342.8	540.1	410.9	462.7	904	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400C9-625AXSP04	389.2	607.6	465.9	522.8	1004.9	391.3	604.3	464.8	519.8	991.9	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400C9-632AXSP04	369.8	584.3	445.8	501.1	974.2	371.5	580.8	444	498.6	961.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400C9-632AXSP04	369.8	584.3	445.8	501.1	974.2	371.5	580.8	444	498.6	961.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400K3-425AXSP04	316.1	503	380.5	430.2	-	317.4	499.8	379.6	428.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400K3-432AXSP04	292.5	468.8	354	400.6	-	293.7	466.3	352.9	398.2	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400K3-525AXSP04	350.7	551.2	420.2	473.2	920.6	351.8	547.9	419.2	470.9	908.9	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400K3-532AXSP04	328.6	522.7	396.7	447.7	879.1	330.2	519.9	395.5	445.1	869	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400K3-625AXSP04	374.5	584.6	448.2	502.7	964.8	376.1	580.7	446.5	499.8	951.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400K3-632AXSP04	355.4	561.4	428.2	481.8	934.9	357.4	557.8	426.9	479.3	922.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400K9-425AXSP04	316.1	503	380.5	430.2	-	317.4	499.8	379.6	428.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400K9-432AXSP04	292.5	468.8	354	400.6	-	293.7	466.3	352.9	398.2	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400K9-525AXSP04	350.7	551.2	420.2	473.2	920.6	351.8	547.9	419.2	470.9	908.9	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400K9-532AXSP04	328.6	522.7	396.7	447.7	879.1	330.2	519.9	395.5	445.1	869	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400K9-625AXSP04	374.5	584.6	448.2	502.7	964.8	376.1	580.7	446.5	499.8	951.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400K9-632AXSP04	355.4	561.4	428.2	481.8	934.9	357.4	557.8	426.9	479.3	922.7	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB400R3-425AXSP04	321.2	510.9	386.8	437.5	-	322.8	508	386.2	435.6	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400R3-432AXSP04	297.5	476.6	360	406.9	-	298.9	474.2	359.3	405.5	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB400R3-525AXSP04	356.2	561	427.5	480.7	936.2	358	557.1	426	478.6	924.6	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400R3-532AXSP04	333.9	531.5	403.2	455.1	894.5	335.7	528.2	402.2	452.7	883.4	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB400R3-625AXSP04	380.6	593.6	455.5	511	980.1	382.3	589.9	454	507.6	967.9	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD																			

EAW-VD1556PB550C9-525AXSP04	408.2	644.8	490.3	552.5	-	410.4	641.1	489.2	550	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550C9-532AXSP04	381.8	607.7	459.8	519.3	-	383.1	604.5	459.2	517.3	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550C9-625AXSP04	439.4	686.4	524.5	589.4	-	441	682.2	523.7	586.4	1125.8	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550C9-632AXSP04	415.5	656.2	499.4	562.2	1098.1	417.5	652.4	498.2	559.5	1085.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K2-425AXSP04	349.1	557.4	421.1	476.2	-	351.4	555	421	474.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K2-432AXSP04	322.9	518.1	390.8	443	-	324.3	516.2	390.4	441.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K2-525AXSP04	388.9	613.5	466.7	525.5	-	390.8	609.9	465.6	523	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K2-532AXSP04	364	579.7	438.8	496	-	366.6	576.7	438.3	494.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K2-625AXSP04	416.7	651.5	498.6	559.9	1079.1	419.2	647.2	496.8	556.8	1065.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K2-632AXSP04	394.8	623.9	474.9	535.1	1043.7	397.1	620.9	474.3	532.3	1031.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K3-425AXSP04	349.1	557.4	421.1	476.2	-	351.4	555	421	474.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K3-432AXSP04	322.9	518.1	390.8	443	-	324.3	516.2	390.4	441.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K3-525AXSP04	388.9	613.5	466.7	525.5	-	390.8	609.9	465.6	523	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K3-532AXSP04	364	579.7	438.8	496	-	366.6	576.7	438.3	494.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K3-625AXSP04	416.7	651.5	498.6	559.9	1079.1	419.2	647.2	496.8	556.8	1065.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K3-632AXSP04	394.8	623.9	474.9	535.1	1043.7	397.1	620.9	474.3	532.3	1031.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K4-425AXSP04	349.1	557.4	421.1	476.2	-	351.4	555	421	474.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K4-432AXSP04	322.9	518.1	390.8	443	-	324.3	516.2	390.4	441.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K4-525AXSP04	388.9	613.5	466.7	525.5	-	390.8	609.9	465.6	523	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K4-532AXSP04	364	579.7	438.8	496	-	366.6	576.7	438.3	494.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K4-625AXSP04	416.7	651.5	498.6	559.9	1079.1	419.2	647.2	496.8	556.8	1065.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K4-632AXSP04	394.8	623.9	474.9	535.1	1043.7	397.1	620.9	474.3	532.3	1031.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K5-425AXSP04	349.1	557.4	421.1	476.2	-	351.4	555	421	474.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K5-432AXSP04	322.9	518.1	390.8	443	-	324.3	516.2	390.4	441.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K5-432AXSP04	388.9	613.5	466.7	525.5	-	390.8	609.9	465.6	523	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K5-532AXSP04	364	579.7	438.8	496	-	366.6	576.7	438.3	494.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K5-625AXSP04	416.7	651.5	498.6	559.9	1079.1	419.2	647.2	496.8	556.8	1065.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K5-632AXSP04	394.8	623.9	474.9	535.1	1043.7	397.1	620.9	474.3	532.3	1031.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K8-425AXSP04	349.1	557.4	421.1	476.2	-	351.4	555	421	474.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K8-432AXSP04	322.9	518.1	390.8	443	-	324.3	516.2	390.4	441.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K8-525AXSP04	388.9	613.5	466.7	525.5	-	390.8	609.9	465.6	523	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K8-532AXSP04	364	579.7	438.8	496	-	366.6	576.7	438.3	494.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K8-625AXSP04	416.7	651.5	498.6	559.9	1079.1	419.2	647.2	496.8	556.8	1065.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K8-632AXSP04	394.8	623.9	474.9	535.1	1043.7	397.1	620.9	474.3	532.3	1031.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K9-425AXSP04	349.1	557.4	421.1	476.2	-	351.4	555	421	474.8	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K9-432AXSP04	322.9	518.1	390.8	443	-	324.3	516.2	390.4	441.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550K9-525AXSP04	388.9	613.5	466.7	525.5	-	390.8	609.9	465.6	523	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K9-532AXSP04	364	579.7	438.8	496	-	366.6	576.7	438.3	494.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550K9-625AXSP04	416.7	651.5	498.6	559.9	1079.1	419.2	647.2	496.8	556.8	1065.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550K9-632AXSP04	394.8	623.9	474.9	535.1	1043.7	397.1	620.9	474.3	532.3	1031.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550R3-425AXSP04	357.8	571.2	431.8	487.6	-	359.6	568	431.1	486.4	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550R3-432AXSP04	330.3	531	399.9	453.4	-	332.3	528.3	399.8	452	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB550R3-525AXSP04	398.5	628.5	477.6	538	-	400.1	625.1	476.8	536.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550R3-532AXSP04	373	593.8	449.8	507.8	-	375.1	591	448.7	506	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB550R3-625AXSP04	426.9	667.1	510.1	573	1105.7	429	663.8	509.3	570.9	1093.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB550R3-632AXSP04	404.4	638.9	486.6	547.6	1069.5	407	636.1	485.5	545.9	1057.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C2-425AXSP04	386.2	617.9	466.8	528.1	-	388.6	616.3	466.8	526.5	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750C2-432AXSP04	355.9	574.2	431.4	489.5	-	357.9	571	431.5	488	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750C2-525AXSP04	430.7	681.4	516.9	583	-	433.3	678.9	517	581.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750C2-532AXSP04	403.1	643	486.1	549.6	-	405.3	639.8	485.5	547.5	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750C2-625AXSP04	462.2	722.7	552.1	620.8	-	465	720	551.7	619	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C2-632AXSP04	438.5	692.5	526.6	593.4	-	440.8	689.6	526.4	591.6	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C3-425AXSP04	386.2	617.9	466.8	528.1	-	388.6	616.3	466.8	526.5	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750C3-432AXSP04	355.9	574.2	431.4	489.5	-	357.9	571	431.5	488	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750C3-525AXSP04	430.7	681.4	516.9	583	-	433.3	678.9	517	581.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750C3-532AXSP04	403.1	643	486.1	549.6	-	405.3	639.8	485.5	547.5	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750C3-625AXSP04	462.2	722.7	552.1	620.8	-	465	720	551.7	619	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C3-632AXSP04	438.5	692.5	526.6	593.4	-	440.8	689.6	526.4	591.6	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C4-425AXSP04	386.2	617.9	466.8	528.1	-	388.6	616.3	466.8	526.5	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750C4-432AXSP04	355.9	574.2	431.4	489.5	-	357.9	571	431.5	488	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750C4-525AXSP04	430.7	681.4	516.9	583	-	433.3	678.9	517	581.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750C4-532AXSP04	403.1	643	486.1	549.6	-	405.3	639.8	485.5	547.5	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750C4-625AXSP04	462.2	722.7	552.1	620.8	-	465	720	551.7	619	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C4-632AXSP04	438.5	692.5	526.6	593.4	-	440.8	689.6	526.4	591.6	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750C5-425AXSP04	386.2	617.9	466.8	528.1	-	388.6	616.3	4											

EAW-VD1556PB750K5-432AXSP04	345.4	555.7	418.3	474.2	-	347.4	553.8	418.4	472.9	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750K5-525AXSP04	416	657.9	499.9	563.5	-	418.9	655	499.5	561.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750K5-532AXSP04	389.8	621.4	469.6	530.7	-	391.8	618.1	469.9	529.4	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750K5-625AXSP04	446.9	697.8	533.6	599.8	-	449.4	695.8	533.1	597.9	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750K5-632AXSP04	423.2	669.2	508.8	573	1120.5	425.7	665.9	508.1	570.9	1108.6	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750K8-425AXSP04	373.6	598.2	451.1	511	-	375.8	595.6	451	509.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750K8-432AXSP04	345.4	555.7	418.3	474.2	-	347.4	553.8	418.4	472.9	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750K8-525AXSP04	416	657.9	499.9	563.5	-	418.9	655	499.5	561.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750K8-532AXSP04	389.8	621.4	469.6	530.7	-	391.8	618.1	469.9	529.4	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750K8-625AXSP04	446.9	697.8	533.6	599.8	-	449.4	695.8	533.1	597.9	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750K8-632AXSP04	423.2	669.2	508.8	573	1120.5	425.7	665.9	508.1	570.9	1108.6	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750K9-425AXSP04	373.6	598.2	451.1	511	-	375.8	595.6	451	509.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750K9-432AXSP04	345.4	555.7	418.3	474.2	-	347.4	553.8	418.4	472.9	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750K9-525AXSP04	416	657.9	499.9	563.5	-	418.9	655	499.5	561.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750K9-532AXSP04	389.8	621.4	469.6	530.7	-	391.8	618.1	469.9	529.4	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750K9-625AXSP04	446.9	697.8	533.6	599.8	-	449.4	695.8	533.1	597.9	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750K9-632AXSP04	423.2	669.2	508.8	573	1120.5	425.7	665.9	508.1	570.9	1108.6	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750R3-425AXSP04	366.1	584.8	442.2	499.7	-	367.8	583	442	498	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750R3-432AXSP04	338.2	544.9	409.9	464.5	-	340.5	543	409.9	463.5	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD1556PB750R3-525AXSP04	407.4	643.3	488.4	551.3	-	409.3	640.4	488	549.4	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750R3-532AXSP04	381.5	607.4	460.3	519.9	-	384.1	605.1	459.6	518.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD1556PB750R3-625AXSP04	436.3	681.5	520.8	585.2	-	439.2	678.4	520.8	584	1119.4	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PB750R3-632AXSP04	413.8	653.6	497.3	560.8	1095	416.2	651.2	497.4	558.6	1083.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD1556PK370C2-425AXSP04	351.3	554.6	420.9	474.8	-	351.5	550.4	419.3	471.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C2-432AXSP04	324.4	515.9	390.3	441.3	-	325.1	512.5	388.6	438.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C2-525AXSP04	391.4	610	466.4	524.1	-	391.4	605	464	520.3	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C2-532AXSP04	366.8	576.9	439.3	494.6	-	367.1	572.1	437.2	491	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C2-625AXSP04	419.7	647.6	498.3	557.9	1064.1	419.6	641.8	495.3	553.5	1048.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C2-632AXSP04	397.9	621.4	475.3	533.7	1029.8	398.4	616	473.4	530.4	1015.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C4-425AXSP04	351.3	554.6	420.9	474.8	-	351.5	550.4	419.3	471.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C4-432AXSP04	324.4	515.9	390.3	441.3	-	325.1	512.5	388.6	438.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C4-525AXSP04	391.4	610	466.4	524.1	-	391.4	605	464	520.3	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C4-532AXSP04	366.8	576.9	439.3	494.6	-	367.1	572.1	437.2	491	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C4-625AXSP04	419.7	647.6	498.3	557.9	1064.1	419.6	641.8	495.3	553.5	1048.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C4-632AXSP04	397.9	621.4	475.3	533.7	1029.8	398.4	616	473.4	530.4	1015.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C5-425AXSP04	351.3	554.6	420.9	474.8	-	351.5	550.4	419.3	471.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C5-432AXSP04	324.4	515.9	390.3	441.3	-	325.1	512.5	388.6	438.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C5-432AXSP04	324.4	515.9	390.3	441.3	-	325.1	512.5	388.6	438.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C5-525AXSP04	391.4	610	466.4	524.1	-	391.4	605	464	520.3	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C5-532AXSP04	366.8	576.9	439.3	494.6	-	367.1	572.1	437.2	491	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C5-625AXSP04	419.7	647.6	498.3	557.9	1064.1	419.6	641.8	495.3	553.5	1048.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C5-632AXSP04	397.9	621.4	475.3	533.7	1029.8	398.4	616	473.4	530.4	1015.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C8-425AXSP04	351.3	554.6	420.9	474.8	-	351.5	550.4	419.3	471.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C8-432AXSP04	324.4	515.9	390.3	441.3	-	325.1	512.5	388.6	438.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370C8-525AXSP04	391.4	610	466.4	524.1	-	391.4	605	464	520.3	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C8-532AXSP04	366.8	576.9	439.3	494.6	-	367.1	572.1	437.2	491	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370C8-625AXSP04	419.7	647.6	498.3	557.9	1064.1	419.6	641.8	495.3	553.5	1048.4	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C8-632AXSP04	397.9	621.4	475.3	533.7	1029.8	398.4	616	473.4	530.4	1015.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370C8-632AXSP04	397.9	621.4	475.3	533.7	1029.8	398.4	616	473.4	530.4	1015.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370K2-425AXSP04	338.4	533	405.1	456.7	-	338.4	528.8	403.5	453.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370K2-432AXSP04	313.3	497.8	376.5	425.4	-	313.2	493.5	374.8	422.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370K2-525AXSP04	376.2	586.1	448.1	503.2	-	376.6	581	445.6	499.4	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370K2-532AXSP04	352.5	555.1	422.7	475.6	928.6	352.8	550.4	420.6	472	915.2	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370K2-625AXSP04	402.4	621	477.7	534.6	1018.3	402.8	615.2	475.3	530.9	1004.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370K2-632AXSP04	382.1	596.5	456.8	512.7	988.8	382.9	591.9	454.8	509.3	973.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370K4-425AXSP04	338.4	533	405.1	456.7	-	338.4	528.8	403.5	453.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370K4-432AXSP04	313.3	497.8	376.5	425.4	-	313.2	493.5	374.8	422.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370K4-525AXSP04	376.2	586.1	448.1	503.2	-	376.6	581	445.6	499.4	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370K4-532AXSP04	352.5	555.1	422.7	475.6	928.6	352.8	550.4	420.6	472	915.2	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370K4-625AXSP04	402.4	621	477.7	534.6	1018.3	402.8	615.2	475.3	530.9	1004.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370K4-632AXSP04	382.1	596.5	456.8	512.7	988.8	382.9	591.9	454.8	509.3	973.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK370K5-425AXSP04	338.4	533	405.1	456.7	-	338.4	528.8	403.5	453.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370K5-432AXSP04	313.3	497.8	376.5	425.4	-	313.2	493.5	374.8	422.3	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK370K5-525AXSP04	376.2	586.1	448.1	503.2	-	376.6	581	445.6	499.4	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK370K5-532AXSP04	352.5	555.1	422.7	475.6	928.6	352.8	550.4	420.6	472	915.2	564	22.7	4"	451	17.				

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1556PK400R3-425AXSP04	344	543.4	412.8	465.4	-	344.9	539.4	410.6	462.6	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK400R3-432AXSP04	318.8	506.8	383.8	433.7	-	319.2	501.7	382.2	430.8	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK400R3-525AXSP04	382.7	595.9	455.9	512.1	-	383.3	592.8	453.6	508.4	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK400R3-532AXSP04	359	565	430.5	484.5	-	359.4	560.4	428.6	481.2	933.7	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK400R3-625AXSP04	409.6	631.5	486.2	544.3	1037.2	409.6	626	483.3	540	1022.1	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK400R3-632AXSP04	389.2	607.1	465.4	522.4	1006.8	389.6	601.9	462.8	518.4	991.7	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500R3-425AXSP04	373.6	591.3	449	506.2	-	374.5	587.7	447.3	502.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500R3-432AXSP04	345.3	550.2	416.2	470.5	-	346.2	546.5	414.6	468	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500R3-525AXSP04	415.6	649.6	495.6	557.4	-	416.3	645.2	493.9	554.2	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500R3-532AXSP04	390.2	615	467.9	527.2	-	390.8	611.1	465.9	523.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500R3-625AXSP04	445.5	687.8	528.5	592.1	-	445.8	683.2	526.5	588.6	1118.7	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500R3-632AXSP04	423.5	661.1	505.4	567.9	1099	424	656.4	503.4	564.4	1085.2	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C2-425AXSP04	391.6	620.7	471.1	531.6	-	392.5	616.7	469.1	527.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C2-432AXSP04	360.9	575.3	435	492.2	-	361.4	572.3	433.4	489.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C2-525AXSP04	438.9	686.9	523.8	589.6	-	439.5	681.9	521.7	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C2-532AXSP04	409.8	646.8	491	553.8	-	410.2	642.2	489.3	550.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C2-625AXSP04	473.5	732	562.1	630.2	-	473.5	726.3	559.4	625.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C2-632AXSP04	447.8	698.9	534	600.5	-	448.2	693.4	531.6	596.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C3-425AXSP04	391.6	620.7	471.1	531.6	-	392.5	616.7	469.1	527.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C3-432AXSP04	360.9	575.3	435	492.2	-	361.4	572.3	433.4	489.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C3-525AXSP04	438.9	686.9	523.8	589.6	-	439.5	681.9	521.7	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C3-532AXSP04	409.8	646.8	491	553.8	-	410.2	642.2	489.3	550.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C3-625AXSP04	473.5	732	562.1	630.2	-	473.5	726.3	559.4	625.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C3-632AXSP04	447.8	698.9	534	600.5	-	448.2	693.4	531.6	596.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C4-425AXSP04	391.6	620.7	471.1	531.6	-	392.5	616.7	469.1	527.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C4-432AXSP04	360.9	575.3	435	492.2	-	361.4	572.3	433.4	489.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C4-525AXSP04	438.9	686.9	523.8	589.6	-	439.5	681.9	521.7	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C4-532AXSP04	409.8	646.8	491	553.8	-	410.2	642.2	489.3	550.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C4-625AXSP04	473.5	732	562.1	630.2	-	473.5	726.3	559.4	625.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C4-632AXSP04	447.8	698.9	534	600.5	-	448.2	693.4	531.6	596.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C5-425AXSP04	391.6	620.7	471.1	531.6	-	392.5	616.7	469.1	527.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C5-432AXSP04	360.9	575.3	435	492.2	-	361.4	572.3	433.4	489.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C5-525AXSP04	438.9	686.9	523.8	589.6	-	439.5	681.9	521.7	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C5-532AXSP04	409.8	646.8	491	553.8	-	410.2	642.2	489.3	550.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C5-625AXSP04	473.5	732	562.1	630.2	-	473.5	726.3	559.4	625.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C5-632AXSP04	447.8	698.9	534	600.5	-	448.2	693.4	531.6	596.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C8-425AXSP04	391.6	620.7	471.1	531.6	-	392.5	616.7	469.1	527.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C8-432AXSP04	360.9	575.3	435	492.2	-	361.4	572.3	433.4	489.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C8-525AXSP04	438.9	686.9	523.8	589.6	-	439.5	681.9	521.7	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C8-532AXSP04	409.8	646.8	491	553.8	-	410.2	642.2	489.3	550.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C8-625AXSP04	473.5	732	562.1	630.2	-	473.5	726.3	559.4	625.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C8-632AXSP04	447.8	698.9	534	600.5	-	448.2	693.4	531.6	596.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C9-425AXSP04	391.6	620.7	471.1	531.6	-	392.5	616.7	469.1	527.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C9-432AXSP04	360.9	575.3	435	492.2	-	361.4	572.3	433.4	489.4	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500C9-525AXSP04	438.9	686.9	523.8	589.6	-	439.5	681.9	521.7	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C9-532AXSP04	409.8	646.8	491	553.8	-	410.2	642.2	489.3	550.5	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500C9-625AXSP04	473.5	732	562.1	630.2	-	473.5	726.3	559.4	625.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500C9-632AXSP04	447.8	698.9	534	600.5	-	448.2	693.4	531.6	596.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500K2-425AXSP04	375	593.7	450.8	508.2	-	375.8	589.9	448.8	505.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500K2-432AXSP04	346.4	552.5	417.6	471.6	-	346.8	548.7	416.2	468.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500K2-525AXSP04	418.5	653.4	499.2	561.4	-	419.1	648.7	497.2	558	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500K2-532AXSP04	392.1	618.2	469.4	529	-	392.4	612.8	467.8	525.9	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500K2-625AXSP04	449.9	694.9	533	598	-	450.4	689.4	531.1	593.9	1129	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500K2-632AXSP04	425.8	666	509	571.2	1107.2	426.8	660.9	506.8	567.5	1091.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500K3-425AXSP04	375	593.7	450.8	508.2	-	375.8	589.9	448.8	505.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500K3-432AXSP04	346.4	552.5	417.6	471.6	-	346.8	548.7	416.2	468.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500K3-525AXSP04	418.5	653.4	499.2	561.4	-	419.1	648.7	497.2	558	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500K3-532AXSP04	392.1	618.2	469.4	529	-	392.4	612.8	467.8	525.9	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500K3-625AXSP04	449.9	694.9	533	598	-	450.4	689.4	531.1	593.9	1129	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500K3-632AXSP04	425.8	666	509	571.2	1107.2	426.8	660.9	506.8	567.5	1091.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK500K4-425AXSP04	375	593.7	450.8	508.2	-	375.8	589.9	448.8	505.5	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500K4-432AXSP04	346.4	552.5	417.6	471.6	-	346.8	548.7	416.2	468.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK500K4-525AXSP04	418.5	653.4	499.2	561.4	-	419.1	648.7	497.2	558	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500K4-532AXSP04	392.1	618.2	469.4	529	-	392.4	612.8	467.8	525.9	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK500K4-625AXSP04	449.9	694.9	533	598	-	450.4	689.4	531.1	593.9	1129	676	23.6	4"	541	15.5	4"</			

EAW-VD1556PK750C3-632AXSP04	473.9	742	566.6	636.7	-	475.3	737.5	564.2	633.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C4-425AXSP02	333.3	598.9	432.4	502	1055.8	348.5	602.9	440.4	507	1048	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD1556PK750C4-432AXSP04	383.3	613.4	462.7	523.6	-	384.6	609	461.3	520.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750C4-525AXSP04	465	730.3	556.5	625.9	-	465.9	725.1	554.4	623.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C4-532AXSP04	435	688.1	521.8	589.2	-	435.5	683.3	520.1	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C4-625AXSP04	500.4	776.5	595.3	667.8	-	501.5	772	592.8	663.7	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C4-632AXSP04	473.9	742	566.6	636.7	-	475.3	737.5	564.2	633.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C5-425AXSP02	333.3	598.9	432.4	502	1055.8	348.5	602.9	440.4	507	1048	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD1556PK750C5-432AXSP04	383.3	613.4	462.7	523.6	-	384.6	609	461.3	520.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750C5-525AXSP04	465	730.3	556.5	625.9	-	465.9	725.1	554.4	623.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C5-532AXSP04	435	688.1	521.8	589.2	-	435.5	683.3	520.1	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C5-625AXSP04	500.4	776.5	595.3	667.8	-	501.5	772	592.8	663.7	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C5-632AXSP04	473.9	742	566.6	636.7	-	475.3	737.5	564.2	633.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C8-425AXSP02	333.3	598.9	432.4	502	1055.8	348.5	602.9	440.4	507	1048	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD1556PK750C8-432AXSP04	383.3	613.4	462.7	523.6	-	384.6	609	461.3	520.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750C8-525AXSP04	465	730.3	556.5	625.9	-	465.9	725.1	554.4	623.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C8-532AXSP04	435	688.1	521.8	589.2	-	435.5	683.3	520.1	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C8-625AXSP04	500.4	776.5	595.3	667.8	-	501.5	772	592.8	663.7	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C8-632AXSP04	473.9	742	566.6	636.7	-	475.3	737.5	564.2	633.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C9-425AXSP02	333.3	598.9	432.4	502	1055.8	348.5	602.9	440.4	507	1048	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD1556PK750C9-432AXSP04	383.3	613.4	462.7	523.6	-	384.6	609	461.3	520.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750C9-525AXSP04	465	730.3	556.5	625.9	-	465.9	725.1	554.4	623.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C9-532AXSP04	435	688.1	521.8	589.2	-	435.5	683.3	520.1	585.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750C9-625AXSP04	500.4	776.5	595.3	667.8	-	501.5	772	592.8	663.7	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750C9-632AXSP04	473.9	742	566.6	636.7	-	475.3	737.5	564.2	633.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K2-425AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K2-432AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K2-525AXSP04	449.2	704	536.3	603.9	-	449.9	699.9	535.1	601.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K2-532AXSP04	420.6	665	505	568.9	-	421.9	660.5	503.5	566.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K2-625AXSP04	483.2	748.6	573.7	643.4	-	483.8	742.7	571.7	639.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K2-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K4-425AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K4-432AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K4-525AXSP04	449.2	704	536.3	603.9	-	449.9	699.9	535.1	601.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K4-532AXSP04	420.6	665	505	568.9	-	421.9	660.5	503.5	566.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K4-625AXSP04	483.2	748.6	573.7	643.4	-	483.8	742.7	571.7	639.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K4-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K5-425AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K5-432AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K5-525AXSP04	449.2	704	536.3	603.9	-	449.9	699.9	535.1	601.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K5-532AXSP04	420.6	665	505	568.9	-	421.9	660.5	503.5	566.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K5-625AXSP04	483.2	748.6	573.7	643.4	-	483.8	742.7	571.7	639.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K5-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K8-425AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K8-432AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K8-525AXSP04	449.2	704	536.3	603.9	-	449.9	699.9	535.1	601.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K8-532AXSP04	420.6	665	505	568.9	-	421.9	660.5	503.5	566.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K8-625AXSP04	483.2	748.6	573.7	643.4	-	483.8	742.7	571.7	639.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K8-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K9-425AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K9-432AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K9-525AXSP04	449.2	704	536.3	603.9	-	449.9	699.9	535.1	601.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K9-532AXSP04	420.6	665	505	568.9	-	421.9	660.5	503.5	566.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K9-625AXSP04	483.2	748.6	573.7	643.4	-	483.8	742.7	571.7	639.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K9-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K3-425AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K3-525AXSP04	449.2	704	536.3	603.9	-	449.9	699.9	535.1	601.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K3-532AXSP04	420.6	665	505	568.9	-	421.9	660.5	503.5	566.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD1556PK750K3-625AXSP04	483.2	748.6	573.7	643.4	-	483.8	742.7	571.7	639.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K3-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K4-432AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K4-532AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K4-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD1556PK750K5-432AXSP04	402.8	639.7	484.9	547.4	-	403.8	635.7	482.9	544.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K5-532AXSP04	371.7	593.4	448.4	507.3	-	372.4	590.1	446.9	505.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD1556PK750K5-632AXSP04	458	716.7	546.3	614.6	-	459.1	711.2	544.8	611.5	-	676	23.6	4"	541</					

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1556ZB370K4-625AXSP06	459.4	692.4	537.8	599.3	-	455.7	683.4	531.4	591.2	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB370K4-632AXSP06	436.5	665.7	514	574	-	433.9	657	508.6	567	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB370K5-625AXSP04	363.6	576.9	437.9	493.8	968.9	364.2	572.1	435.9	490.3	954.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB370K5-432AXSP04	335.4	538.3	407.4	460.4	910.8	336.7	533.5	405.4	456.8	898.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB370K5-525AXSP06	427.9	653	504	563.2	-	424.9	644.7	499	556.5	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB370K5-532AXSP06	401.7	619	475.7	533	-	399.3	611.3	470.5	526.9	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB370K5-625AXSP06	459.4	692.4	537.8	599.3	-	455.7	683.4	531.4	591.2	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB370K5-632AXSP06	436.5	665.7	514	574	-	433.9	657	508.6	567	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB370K8-425AXSP04	363.6	576.9	437.9	493.8	968.9	364.2	572.1	435.9	490.3	954.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB370K8-432AXSP04	335.4	538.3	407.4	460.4	910.8	336.7	533.5	405.4	456.8	898.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB370K8-525AXSP06	427.9	653	504	563.2	-	424.9	644.7	499	556.5	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB370K8-532AXSP06	401.7	619	475.7	533	-	399.3	611.3	470.5	526.9	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB370K8-625AXSP06	459.4	692.4	537.8	599.3	-	455.7	683.4	531.4	591.2	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB370K8-632AXSP06	436.5	665.7	514	574	-	433.9	657	508.6	567	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400B3-425AXSP04	368.5	585	443.8	500.6	982.9	369.1	579.4	441.9	497.2	968.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400B3-432AXSP04	339.8	545.9	412.9	466.7	924.1	341.2	541.1	411	463.3	910	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400B3-525AXSP06	433.6	662.1	510.9	571	-	430.7	653.8	505.9	564.3	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400B3-532AXSP06	380.5	606.4	459.8	519.4	1014.9	382.1	601.1	458.2	515.5	1000.1	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB400B3-625AXSP06	464.4	701.1	544.4	605.9	-	461.6	691.6	538.3	598.9	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400B3-632AXSP06	442.3	674.9	520.9	581.8	-	439.8	666.2	515.6	574.8	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400C3-425AXSP04	377.9	598.9	454.6	513	1008.7	378.4	593.8	452.5	509.2	993.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400C3-432AXSP04	347.9	557.6	422.1	476.4	945.1	348.6	553.5	420	473.6	931.6	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400C3-525AXSP06	418.1	658.6	503.2	565	1093.8	419	652.3	500.1	561	1077.6	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB400C3-532AXSP06	417.4	644.2	494.5	554.4	-	414.8	636	489	547.8	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400C3-625AXSP06	479.2	724	561.1	625.5	-	475.4	713.7	555.2	617	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400C3-632AXSP06	454.5	694	535.3	598.1	-	451.2	684.1	529.8	590.8	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400C9-425AXSP04	377.9	598.9	454.6	513	1008.7	378.4	593.8	452.5	509.2	993.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400C9-432AXSP04	347.9	557.6	422.1	476.4	945.1	348.6	553.5	420	473.6	931.6	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400C9-525AXSP06	418.1	658.6	503.2	565	1093.8	419	652.3	500.1	561	1077.6	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB400C9-532AXSP06	417.4	644.2	494.5	554.4	-	414.8	636	489	547.8	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400C9-625AXSP06	479.2	724	561.1	625.5	-	475.4	713.7	555.2	617	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400K9-532AXSP06	454.5	694	535.3	598.1	-	451.2	684.1	529.8	590.8	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400K3-425AXSP04	363.6	576.9	437.9	493.8	968.9	364.2	572.1	435.9	490.3	954.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400K3-432AXSP04	335.4	538.3	407.4	460.4	910.8	336.7	533.5	405.4	456.8	898.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400K3-525AXSP06	427.9	653	504	563.2	-	424.9	644.7	499	556.5	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400K3-532AXSP06	401.7	619	475.7	533	-	399.3	611.3	470.5	526.9	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400K3-625AXSP06	459.4	692.4	537.8	599.3	-	455.7	683.4	531.4	591.2	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400K3-632AXSP06	436.5	665.7	514	574	-	433.9	657	508.6	567	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400K9-425AXSP04	363.6	576.9	437.9	493.8	968.9	364.2	572.1	435.9	490.3	954.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400K9-432AXSP04	335.4	538.3	407.4	460.4	910.8	336.7	533.5	405.4	456.8	898.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400K9-525AXSP06	427.9	653	504	563.2	-	424.9	644.7	499	556.5	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400K9-532AXSP06	401.7	619	475.7	533	-	399.3	611.3	470.5	526.9	-	507	33.2	3"	406	21.9	3"	609	41.9	4"
EAW-VD1556ZB400K9-625AXSP06	459.4	692.4	537.8	599.3	-	455.7	683.4	531.4	591.2	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400K9-632AXSP06	436.5	665.7	514	574	-	433.9	657	508.6	567	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400R3-425AXSP04	370.7	588.8	447.3	504.5	989.5	372	584.1	444.7	500.4	975.6	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400R3-432AXSP04	342.5	549.5	415.4	469.7	930.6	343.4	544.8	413.6	466.3	916.6	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB400R3-525AXSP06	409.3	644.3	492.6	553.7	1070.9	410.9	639.2	489.7	549.2	1054.1	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB400R3-532AXSP06	383.4	610.3	463.3	523.4	1021.7	384.4	605	461.1	519.5	1006.9	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB400R3-625AXSP06	468.6	706.7	548.6	611.5	-	465	697.7	542.3	603.4	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB400R3-632AXSP06	445.6	679	524.7	586.1	-	442.4	670.4	518.7	578.4	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550B3-425AXSP04	405.6	644.4	488.5	550.9	-	406.9	638.8	486.2	547.7	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550B3-432AXSP04	373.5	599.1	452.8	511.8	-	374.7	594.6	451.3	508.6	1003.9	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550B3-525AXSP06	449.2	706.8	539.6	606.3	1177.8	450.2	701.1	537	602.1	1161.8	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550B3-532AXSP04	419.4	667.7	507.7	572.5	1122.9	421.1	662.7	505	568	1106.2	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550B3-625AXSP06	512.4	776.8	601.9	670.5	-	509.5	767.3	596	663.6	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550B3-632AXSP06	487.3	745	574.3	642.1	-	484.5	736.4	569.2	635.2	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550C2-425AXSP04	424.1	673.5	510.4	576.1	-	424.7	668.5	507.8	572.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550C2-432AXSP04	389.4	624.3	471.7	533.6	-	390.9	619.4	470.1	530.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550C2-525AXSP04	473.1	744	567	638.5	1243.2	474.1	737.6	564.1	633.8	1224.1	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550C2-532AXSP04	439.1	699.9	531.1	599.4	1177.2	440.8	694.2	528.9	594.3	1160.4	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550C2-625AXSP04	511.1	798.2	612.5	687.1	1317.7	512.5	790.7	608.6	681.4	1297.3	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB550C2-632AXSP06	512.1	784.4	603.7	676.3	-	508.9	774.9	598.1	667.8	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550C3-425AXSP04	424.1	673.5	510.4	576.1	-	424.7	668.5	507.8	572.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550C3-432AXSP04	389.4	624.3	471.7	533.6	-	390.9	619.4												

EAW-VD1556ZB550K3-532AXSP04	420.8	669	508.5	573.4	1125.1	421.7	663.8	506.6	569.8	1109.7	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K3-625AXSP06	515.5	781.5	604.7	674.5	-	512	771.2	598.9	666.9	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K3-632AXSP06	488.9	747.6	576.2	644.2	-	485.9	738.7	570.9	637.1	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K4-425AXSP04	406.9	645.4	489.2	552.7	-	407.5	640.9	487.8	548.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K4-432AXSP04	374.4	600.2	453.5	512.6	-	376.1	595.8	452.1	510.5	1006.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K4-525AXSP04	450.6	709.2	541.3	609.2	1183.4	452.2	703.2	538.6	604.8	1165.5	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K4-532AXSP04	420.8	669	508.5	573.4	1125.1	421.7	663.8	506.6	569.8	1109.7	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K4-625AXSP06	515.5	781.5	604.7	674.5	-	512	771.2	598.9	666.9	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K4-632AXSP06	488.9	747.6	576.2	644.2	-	485.9	738.7	570.9	637.1	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K5-425AXSP04	406.9	645.4	489.2	552.7	-	407.5	640.9	487.8	548.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K5-432AXSP04	374.4	600.2	453.5	512.6	-	376.1	595.8	452.1	510.5	1006.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K5-525AXSP04	450.6	709.2	541.3	609.2	1183.4	452.2	703.2	538.6	604.8	1165.5	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K5-532AXSP04	420.8	669	508.5	573.4	1125.1	421.7	663.8	506.6	569.8	1109.7	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K5-625AXSP06	515.5	781.5	604.7	674.5	-	512	771.2	598.9	666.9	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K5-632AXSP06	488.9	747.6	576.2	644.2	-	485.9	738.7	570.9	637.1	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K8-425AXSP04	406.9	645.4	489.2	552.7	-	407.5	640.9	487.8	548.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K8-432AXSP04	374.4	600.2	453.5	512.6	-	376.1	595.8	452.1	510.5	1006.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K8-525AXSP04	450.6	709.2	541.3	609.2	1183.4	452.2	703.2	538.6	604.8	1165.5	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K8-532AXSP04	420.8	669	508.5	573.4	1125.1	421.7	663.8	506.6	569.8	1109.7	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K8-625AXSP06	515.5	781.5	604.7	674.5	-	512	771.2	598.9	666.9	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K8-632AXSP06	488.9	747.6	576.2	644.2	-	485.9	738.7	570.9	637.1	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K9-425AXSP04	406.9	645.4	489.2	552.7	-	407.5	640.9	487.8	548.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K9-432AXSP04	374.4	600.2	453.5	512.6	-	376.1	595.8	452.1	510.5	1006.1	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550K9-525AXSP04	450.6	709.2	541.3	609.2	1183.4	452.2	703.2	538.6	604.8	1165.5	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K9-532AXSP04	420.8	669	508.5	573.4	1125.1	421.7	663.8	506.6	569.8	1109.7	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550K9-625AXSP06	515.5	781.5	604.7	674.5	-	512	771.2	598.9	666.9	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550K9-632AXSP06	488.9	747.6	576.2	644.2	-	485.9	738.7	570.9	637.1	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB550R3-425AXSP04	417.3	663.1	502.9	567.4	-	418.9	658.8	500.8	564.5	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550R3-432AXSP04	384.9	616.4	466	527	-	386.2	613.2	463.9	524.1	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB550R3-525AXSP04	463.8	729.7	556.5	625.6	1217.1	465	723.9	554	621.4	1200.6	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550R3-532AXSP04	432.3	688.3	522.7	588.7	1157.1	433.5	683.3	520.1	585.2	1141.6	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB550R3-625AXSP04	499.7	779.8	597.9	670.6	1286.6	501	773.3	595.6	666.6	1268.2	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB550R3-632AXSP06	501.9	769.3	592.4	662.6	-	499.1	759.4	586.4	655.5	-	609	30.6	4"	487	23.3	3"	730	42.9	4"
EAW-VD1556ZB750C2-425AXSP04	453.7	722.4	546.7	617.9	-	455.2	718.4	545	614.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C2-432AXSP04	417.7	669.9	505	572.4	-	418.8	665.7	503.3	568.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C2-525AXSP04	506.9	797.4	607.1	683.3	-	508.1	792	605.1	679.5	-	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C2-532AXSP04	471	750	568.4	642.2	-	472.9	745.3	566.1	637.9	1249	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C2-625AXSP04	547.6	855.1	655	735.3	1415.6	549.4	848.5	652	730.4	1395.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C2-632AXSP04	516	815.4	621.4	699.8	1360.7	517.7	809.4	619	695.5	1343.2	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C3-425AXSP04	453.7	722.4	546.7	617.9	-	455.2	718.4	545	614.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C3-432AXSP04	417.7	669.9	505	572.4	-	418.8	665.7	503.3	568.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C3-525AXSP04	506.9	797.4	607.1	683.3	-	508.1	792	605.1	679.5	-	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C3-532AXSP04	471	750	568.4	642.2	-	472.9	745.3	566.1	637.9	1249	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C3-625AXSP04	547.6	855.1	655	735.3	1415.6	549.4	848.5	652	730.4	1395.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C3-632AXSP04	516	815.4	621.4	699.8	1360.7	517.7	809.4	619	695.5	1343.2	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C4-425AXSP04	453.7	722.4	546.7	617.9	-	455.2	718.4	545	614.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C4-432AXSP04	417.7	669.9	505	572.4	-	418.8	665.7	503.3	568.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C4-525AXSP04	506.9	797.4	607.1	683.3	-	508.1	792	605.1	679.5	-	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C4-532AXSP04	471	750	568.4	642.2	-	472.9	745.3	566.1	637.9	1249	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C4-625AXSP04	547.6	855.1	655	735.3	1415.6	549.4	848.5	652	730.4	1395.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C4-632AXSP04	516	815.4	621.4	699.8	1360.7	517.7	809.4	619	695.5	1343.2	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C5-425AXSP04	453.7	722.4	546.7	617.9	-	455.2	718.4	545	614.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C5-432AXSP04	417.7	669.9	505	572.4	-	418.8	665.7	503.3	568.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C5-525AXSP04	506.9	797.4	607.1	683.3	-	508.1	792	605.1	679.5	-	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C5-532AXSP04	471	750	568.4	642.2	-	472.9	745.3	566.1	637.9	1249	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C5-625AXSP04	547.6	855.1	655	735.3	1415.6	549.4	848.5	652	730.4	1395.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C5-632AXSP04	516	815.4	621.4	699.8	1360.7	517.7	809.4	619	695.5	1343.2	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C8-425AXSP04	453.7	722.4	546.7	617.9	-	455.2	718.4	545	614.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C8-432AXSP04	417.7	669.9	505	572.4	-	418.8	665.7	503.3	568.6	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750C8-525AXSP04	506.9	797.4	607.1	683.3	-	508.1	792	605.1	679.5	-	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C8-532AXSP04	471	750	568.4	642.2	-	472.9	745.3	566.1	637.9	1249	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750C8-625AXSP04	547.6	855.1	655	735.3	1415.6	549.4	848.5	652	730.4	1395.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750C8-632AXSP04	516	815.4	621.4	699.8	1360.7	517.7	809.4	619	695.5	1343.2	913	20.1							

EAW-VD1556ZB750K9-525AXSP04	489.3	769.5	585.7	659.9	-	490.2	763.9	583.6	656	-	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750K9-532AXSP04	455.6	725.2	549.5	620.5	1221.6	457.4	719.4	548.2	616.3	1204.4	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750K9-625AXSP04	527.4	823.3	630.5	707.5	1360.1	528.5	816.3	627.8	703	1341.7	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750K9-632AXSP04	498.2	787.1	599.6	675	1312	499.7	781	597.1	670.6	1293	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750R3-425AXSP04	430	684.6	517.6	585.4	-	431.3	679.5	516.8	581.8	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750R3-432AXSP04	397	636.5	479.6	542.8	-	398.3	631.5	478.7	540.2	-	609	21.1	4"	487	17.1	3"	730	29.7	4"
EAW-VD1556ZB750R3-525AXSP04	477.6	752.6	573.3	644.8	1256.2	479.2	746	571.2	640.8	1238.5	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750R3-532AXSP04	445.3	709.2	537.8	607.1	1193.6	447.7	704.5	536.5	603.9	1178.4	755	22.4	4"	604	14.7	4"	906	27.6	(2) 4"
EAW-VD1556ZB750R3-625AXSP04	514	803	615.3	690.3	1325.7	515.8	797	613.4	685.8	1307.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZB750R3-632AXSP04	486.4	768.8	586.1	659.6	1280.7	488.5	762.8	583.6	655.2	1263.8	913	20.1	(2) 4"	730	15.8	4"	1096	28.2	(2) 4"
EAW-VD1556ZK017G7-425AXSP02	459.4	825.4	595.1	691.4	1454.2	478.9	828.1	604.8	697	1440.8	1217	12.7	(2) 4"	974	8.4	(2) 4"	1461	17.9	(2) 4"
EAW-VD1556ZK017G7-432AXSP04	522.7	836.5	631.2	714.4	-	523	829.5	628.2	709.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK017G7-525AXSP04	646.3	1016	774	871.2	-	646.2	1007.9	769.4	863.9	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK017G7-532AXSP04	596.9	946.3	717.8	809.5	-	596.8	938.1	713.1	803.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK017G7-625AXSP04	709.2	1102.9	844.2	947.6	-	708.6	1091.4	838	938.7	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK017G7-632AXSP04	662.3	1038.8	792.2	890.8	-	662.8	1030	787.1	884.3	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK370C2-425AXSP04	401.5	629.8	479.7	540.5	-	400.6	623.6	476.7	535	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C2-432AXSP04	369.8	586.9	445.2	502.6	988.3	369.8	580.9	442.3	498.1	973.2	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C2-525AXSP04	444.7	692.5	530.6	595	1143.3	444	683.9	526.3	589	1123.4	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C2-532AXSP04	415.3	653.2	498.7	561	1088.3	414.7	646.3	495.2	554.9	1070.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C2-625AXSP04	479	739.1	569.5	637.5	1206.5	478.3	729.8	564.6	630	1185.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK370C2-632AXSP06	479.6	727.3	562.9	627.5	-	474.6	715.9	555.5	619	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370C4-425AXSP04	401.5	629.8	479.7	540.5	-	400.6	623.6	476.7	535	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C4-432AXSP04	369.8	586.9	445.2	502.6	988.3	369.8	580.9	442.3	498.1	973.2	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C4-525AXSP04	444.7	692.5	530.6	595	1143.3	444	683.9	526.3	589	1123.4	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C4-532AXSP04	415.3	653.2	498.7	561	1088.3	414.7	646.3	495.2	554.9	1070.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C4-625AXSP04	479	739.1	569.5	637.5	1206.5	478.3	729.8	564.6	630	1185.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK370C4-632AXSP06	479.6	727.3	562.9	627.5	-	474.6	715.9	555.5	619	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370C5-425AXSP04	401.5	629.8	479.7	540.5	-	400.6	623.6	476.7	535	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C5-432AXSP04	369.8	586.9	445.2	502.6	988.3	369.8	580.9	442.3	498.1	973.2	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C5-525AXSP04	444.7	692.5	530.6	595	1143.3	444	683.9	526.3	589	1123.4	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C5-532AXSP04	415.3	653.2	498.7	561	1088.3	414.7	646.3	495.2	554.9	1070.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C5-625AXSP04	479	739.1	569.5	637.5	1206.5	478.3	729.8	564.6	630	1185.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK370C5-632AXSP06	479.6	727.3	562.9	627.5	-	474.6	715.9	555.5	619	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370C8-425AXSP04	401.5	629.8	479.7	540.5	-	400.6	623.6	476.7	535	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C8-432AXSP04	369.8	586.9	445.2	502.6	988.3	369.8	580.9	442.3	498.1	973.2	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370C8-525AXSP04	444.7	692.5	530.6	595	1143.3	444	683.9	526.3	589	1123.4	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C8-532AXSP04	415.3	653.2	498.7	561	1088.3	414.7	646.3	495.2	554.9	1070.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370C8-625AXSP04	479	739.1	569.5	637.5	1206.5	478.3	729.8	564.6	630	1185.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK370C8-632AXSP06	479.6	727.3	562.9	627.5	-	474.6	715.9	555.5	619	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K2-425AXSP04	386.8	606.6	462.7	520.2	1013.2	386	600.8	459.2	515.8	997.6	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K2-432AXSP04	356.8	566.3	430.1	485.3	953.7	356.8	560.4	427.3	480.9	937.8	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K2-525AXSP04	426.8	664.4	509.6	571.3	1095.9	426.2	656.4	505.7	565.7	1077.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K2-532AXSP04	400	628.8	480	539.7	1046.6	399.4	622.4	476.8	534.8	1028.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K2-625AXSP06	484.4	725.9	564.7	628.1	-	479.3	714.8	557.4	618.9	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K2-632AXSP06	460.7	697.8	539.9	602.5	-	456.7	687.1	533.6	593.7	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K4-425AXSP04	386.8	606.6	462.7	520.2	1013.2	386	600.8	459.2	515.8	997.6	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K4-432AXSP04	356.8	566.3	430.1	485.3	953.7	356.8	560.4	427.3	480.9	937.8	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K4-525AXSP04	426.8	664.4	509.6	571.3	1095.9	426.2	656.4	505.7	565.7	1077.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K4-532AXSP04	400	628.8	480	539.7	1046.6	399.4	622.4	476.8	534.8	1028.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K4-625AXSP06	484.4	725.9	564.7	628.1	-	479.3	714.8	557.4	618.9	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K4-632AXSP06	460.7	697.8	539.9	602.5	-	456.7	687.1	533.6	593.7	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K5-425AXSP04	386.8	606.6	462.7	520.2	1013.2	386	600.8	459.2	515.8	997.6	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K5-432AXSP04	356.8	566.3	430.1	485.3	953.7	356.8	560.4	427.3	480.9	937.8	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K5-525AXSP04	426.8	664.4	509.6	571.3	1095.9	426.2	656.4	505.7	565.7	1077.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K5-532AXSP04	400	628.8	480	539.7	1046.6	399.4	622.4	476.8	534.8	1028.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K5-625AXSP06	484.4	725.9	564.7	628.1	-	479.3	714.8	557.4	618.9	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K5-632AXSP06	460.7	697.8	539.9	602.5	-	456.7	687.1	533.6	593.7	-	609	33.5	4"	487	25.3	3"	730	47	4"
EAW-VD1556ZK370K8-425AXSP04	386.8	606.6	462.7	520.2	1013.2	386	600.8	459.2	515.8	997.6	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K8-432AXSP04	356.8	566.3	430.1	485.3	953.7	356.8	560.4	427.3	480.9	937.8	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK370K8-525AXSP04	426.8	664.4	509.6	571.3	1095.9	426.2	656.4	505.7	565.7	1077.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK370K8-532AXSP04	400	628.8	480	539.7	1046.6	399.4	622.4	476.8	534.8	1028.8	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"

EAW-VD1556ZK5S0B3-432AXSP04	398.7	632.4	479.8	541.4	-	398.6	626.8	476.5	536.3	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0B3-525AXSP04	479.6	746.9	571.8	641.8	1236.9	479	738.8	567.4	635.5	1217.2	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0B3-532AXSP04	447.7	704.5	537.3	604.2	1176.6	447.8	698.1	533.5	599.4	1159.1	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0B3-625AXSP04	516.9	797.2	614	686.9	1304.5	516.1	788.2	609.6	679.8	1283.8	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0B3-632AXSP04	488.8	763.5	584.9	656	1260.7	488.6	754.9	580.9	650.1	1240.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C2-425AXSP04	450.3	710	540	608.6	-	450.1	702.7	536.5	603.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C2-432AXSP04	414.9	658.6	498.7	563.2	-	414.6	652.3	496	558.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C2-525AXSP04	503.5	783.5	599.7	673.6	-	502.6	775.5	594.7	666.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C2-532AXSP04	468.5	736.6	560.9	632	1232.1	467.8	729.7	557.7	625.9	1213.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C2-625AXSP04	544.8	840.8	647.6	724.8	1380.5	543.9	831.9	642.6	716.9	1356.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C2-632AXSP04	513	801.8	614.2	689.3	1327.2	512.6	792.2	609.7	681.7	1304.6	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C3-425AXSP04	450.3	710	540	608.6	-	450.1	702.7	536.5	603.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C3-432AXSP04	414.9	658.6	498.7	563.2	-	414.6	652.3	496	558.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C3-525AXSP04	503.5	783.5	599.7	673.6	-	502.6	775.5	594.7	666.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C3-532AXSP04	468.5	736.6	560.9	632	1232.1	467.8	729.7	557.7	625.9	1213.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C3-625AXSP04	544.8	840.8	647.6	724.8	1380.5	543.9	831.9	642.6	716.9	1356.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C3-632AXSP04	513	801.8	614.2	689.3	1327.2	512.6	792.2	609.7	681.7	1304.6	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C4-425AXSP04	450.3	710	540	608.6	-	450.1	702.7	536.5	603.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C4-432AXSP04	414.9	658.6	498.7	563.2	-	414.6	652.3	496	558.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C4-525AXSP04	503.5	783.5	599.7	673.6	-	502.6	775.5	594.7	666.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C4-532AXSP04	468.5	736.6	560.9	632	1232.1	467.8	729.7	557.7	625.9	1213.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C5-425AXSP04	544.8	840.8	647.6	724.8	1380.5	543.9	831.9	642.6	716.9	1356.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C5-625AXSP04	513	801.8	614.2	689.3	1327.2	512.6	792.2	609.7	681.7	1304.6	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C5-632AXSP04	450.3	710	540	608.6	-	450.1	702.7	536.5	603.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C8-425AXSP04	414.9	658.6	498.7	563.2	-	414.6	652.3	496	558.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C8-432AXSP04	414.9	658.6	498.7	563.2	-	414.6	652.3	496	558.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C8-525AXSP04	503.5	783.5	599.7	673.6	-	502.6	775.5	594.7	666.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C8-532AXSP04	468.5	736.6	560.9	632	1232.1	467.8	729.7	557.7	625.9	1213.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C9-425AXSP04	544.8	840.8	647.6	724.8	1380.5	543.9	831.9	642.6	716.9	1356.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C9-625AXSP04	513	801.8	614.2	689.3	1327.2	512.6	792.2	609.7	681.7	1304.6	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C9-632AXSP04	450.3	710	540	608.6	-	450.1	702.7	536.5	603.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C9-425AXSP04	414.9	658.6	498.7	563.2	-	414.6	652.3	496	558.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0C9-525AXSP04	503.5	783.5	599.7	673.6	-	502.6	775.5	594.7	666.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C9-532AXSP04	468.5	736.6	560.9	632	1232.1	467.8	729.7	557.7	625.9	1213.3	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0C9-625AXSP04	544.8	840.8	647.6	724.8	1380.5	543.9	831.9	642.6	716.9	1356.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0C9-632AXSP04	513	801.8	614.2	689.3	1327.2	512.6	792.2	609.7	681.7	1304.6	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K2-425AXSP04	433	681	517.9	584.3	-	432.8	674.3	514.7	579.2	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K2-432AXSP04	399.5	633.9	480.8	542.6	-	399.5	628.3	477.6	538.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K2-525AXSP04	481.2	748.4	572.8	643	1239.6	480.5	740.2	569.2	637.5	1219.6	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K2-532AXSP04	449.3	705.9	538.3	606.3	1180.8	448.7	699.6	535.4	600.6	1161.7	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K2-625AXSP04	518.6	800	616.2	689.3	1310.8	517.7	790.7	611.5	682.8	1288.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K2-632AXSP04	490.4	765	585.9	658.2	1264.9	490.2	757.3	581.9	652.2	1244.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K3-425AXSP04	433	681	517.9	584.3	-	432.8	674.3	514.7	579.2	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K3-432AXSP04	399.5	633.9	480.8	542.6	-	399.5	628.3	477.6	538.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K3-525AXSP04	481.2	748.4	572.8	643	1239.6	480.5	740.2	569.2	637.5	1219.6	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K3-532AXSP04	449.3	705.9	538.3	606.3	1180.8	448.7	699.6	535.4	600.6	1161.7	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K3-625AXSP04	518.6	800	616.2	689.3	1310.8	517.7	790.7	611.5	682.8	1288.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K3-632AXSP04	490.4	765	585.9	658.2	1264.9	490.2	757.3	581.9	652.2	1244.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K4-425AXSP04	433	681	517.9	584.3	-	432.8	674.3	514.7	579.2	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K4-432AXSP04	399.5	633.9	480.8	542.6	-	399.5	628.3	477.6	538.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K4-525AXSP04	481.2	748.4	572.8	643	1239.6	480.5	740.2	569.2	637.5	1219.6	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K4-532AXSP04	449.3	705.9	538.3	606.3	1180.8	448.7	699.6	535.4	600.6	1161.7	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K4-625AXSP04	518.6	800	616.2	689.3	1310.8	517.7	790.7	611.5	682.8	1288.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K4-632AXSP04	490.4	765	585.9	658.2	1264.9	490.2	757.3	581.9	652.2	1244.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K5-425AXSP04	433	681	517.9	584.3	-	432.8	674.3	514.7	579.2	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K5-432AXSP04	399.5	633.9	480.8	542.6	-	399.5	628.3	477.6	538.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K5-525AXSP04	481.2	748.4	572.8	643	1239.6	480.5	740.2	569.2	637.5	1219.6	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K5-532AXSP04	449.3	705.9	538.3	606.3	1180.8	448.7	699.6	535.4	600.6	1161.7	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK5S0K5-625AXSP04	518.6	800	616.2	689.3	1310.8	517.7	790.7	611.5	682.8	1288.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K5-632AXSP04	490.4	765	585.9	658.2	1264.9	490.2	757.3	581.9	652.2	1244.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK5S0K8-425AXSP04	433	681	517.9	584.3	-	432.8	674.3	514.7	579.2	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK5S0K8-432AXSP04	399.5	633.9	480.8	542.6	-	399.5	628.3	477.6	538.5	-	609	23.1	4"	487	18.4	3"	73		

EAW-VD1556ZK750C5-425AXSP04	483.4	764.3	580.5	655.1	-	484	757.5	577.6	650	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750C5-432AXSP04	445.3	708.9	535.8	606.1	-	445.7	702.2	533	601.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750C5-525AXSP04	540.8	844.4	644.7	724.8	-	540	836	640.5	718.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750C5-532AXSP04	503.8	794	603.8	680.1	-	503.8	786.4	600.2	674.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750C5-625AXSP04	586.5	904.8	695.6	779.1	1489.8	585.7	896.7	691.4	772.9	1465.7	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750C5-632AXSP04	552.4	862.5	660.1	741.4	1432.4	552.2	854.8	655.4	734.5	1410.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750C8-425AXSP04	483.4	764.3	580.5	655.1	-	484	757.5	577.6	650	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750C8-432AXSP04	445.3	708.9	535.8	606.1	-	445.7	702.2	533	601.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750C8-525AXSP04	540.8	844.4	644.7	724.8	-	540	836	640.5	718.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750C8-532AXSP04	503.8	794	603.8	680.1	-	503.8	786.4	600.2	674.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750C8-625AXSP04	586.5	904.8	695.6	779.1	1489.8	585.7	896.7	691.4	772.9	1465.7	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750C8-632AXSP04	552.4	862.5	660.1	741.4	1432.4	552.2	854.8	655.4	734.5	1410.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750C9-425AXSP04	483.4	764.3	580.5	655.1	-	484	757.5	577.6	650	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750C9-432AXSP04	445.3	708.9	535.8	606.1	-	445.7	702.2	533	601.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750C9-525AXSP04	540.8	844.4	644.7	724.8	-	540	836	640.5	718.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750C9-532AXSP04	503.8	794	603.8	680.1	-	503.8	786.4	600.2	674.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750C9-625AXSP04	586.5	904.8	695.6	779.1	1489.8	585.7	896.7	691.4	772.9	1465.7	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750C9-632AXSP04	552.4	862.5	660.1	741.4	1432.4	552.2	854.8	655.4	734.5	1410.1	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K2-425AXSP04	468.2	740	561.9	633.7	-	468.8	733.5	559.2	629	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K2-432AXSP04	432.5	687.7	520.6	587.3	-	432.5	681.3	517.9	583.7	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K2-525AXSP04	522	813.7	622	699	-	522	806.7	618.8	692.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K2-532AXSP04	487.5	766.9	584	657.4	-	487.6	759.8	580.6	652	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K2-625AXSP04	564.3	871.8	670	750.2	1432.5	564.1	862.6	665.8	743.9	1408.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K2-632AXSP04	533.3	832.5	637	715.1	1379.4	533	823.9	633.3	709.5	1358	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K3-425AXSP04	468.2	740	561.9	633.7	-	468.8	733.5	559.2	629	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K3-432AXSP04	432.5	687.7	520.6	587.3	-	432.5	681.3	517.9	583.7	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K3-525AXSP04	522	813.7	622	699	-	522	806.7	618.8	692.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K3-532AXSP04	487.5	766.9	584	657.4	-	487.6	759.8	580.6	652	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K3-625AXSP04	564.3	871.8	670	750.2	1432.5	564.1	862.6	665.8	743.9	1408.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K3-632AXSP04	533.3	832.5	637	715.1	1379.4	533	823.9	633.3	709.5	1358	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K4-425AXSP04	468.2	740	561.9	633.7	-	468.8	733.5	559.2	629	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K4-432AXSP04	432.5	687.7	520.6	587.3	-	432.5	681.3	517.9	583.7	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K4-525AXSP04	522	813.7	622	699	-	522	806.7	618.8	692.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K4-532AXSP04	487.5	766.9	584	657.4	-	487.6	759.8	580.6	652	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K4-625AXSP04	564.3	871.8	670	750.2	1432.5	564.1	862.6	665.8	743.9	1408.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K4-632AXSP04	533.3	832.5	637	715.1	1379.4	533	823.9	633.3	709.5	1358	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K5-425AXSP04	468.2	740	561.9	633.7	-	468.8	733.5	559.2	629	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K5-432AXSP04	432.5	687.7	520.6	587.3	-	432.5	681.3	517.9	583.7	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K5-525AXSP04	522	813.7	622	699	-	522	806.7	618.8	692.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K5-532AXSP04	487.5	766.9	584	657.4	-	487.6	759.8	580.6	652	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K5-625AXSP04	564.3	871.8	670	750.2	1432.5	564.1	862.6	665.8	743.9	1408.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K5-632AXSP04	533.3	832.5	637	715.1	1379.4	533	823.9	633.3	709.5	1358	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K8-425AXSP04	468.2	740	561.9	633.7	-	468.8	733.5	559.2	629	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K8-432AXSP04	432.5	687.7	520.6	587.3	-	432.5	681.3	517.9	583.7	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K8-525AXSP04	522	813.7	622	699	-	522	806.7	618.8	692.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K8-532AXSP04	487.5	766.9	584	657.4	-	487.6	759.8	580.6	652	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K8-625AXSP04	564.3	871.8	670	750.2	1432.5	564.1	862.6	665.8	743.9	1408.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K8-632AXSP04	533.3	832.5	637	715.1	1379.4	533	823.9	633.3	709.5	1358	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K9-425AXSP04	468.2	740	561.9	633.7	-	468.8	733.5	559.2	629	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K9-432AXSP04	432.5	687.7	520.6	587.3	-	432.5	681.3	517.9	583.7	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750K9-525AXSP04	522	813.7	622	699	-	522	806.7	618.8	692.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K9-532AXSP04	487.5	766.9	584	657.4	-	487.6	759.8	580.6	652	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750K9-625AXSP04	564.3	871.8	670	750.2	1432.5	564.1	862.6	665.8	743.9	1408.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750K9-632AXSP04	533.3	832.5	637	715.1	1379.4	533	823.9	633.3	709.5	1358	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750R3-425AXSP04	458.5	723.7	550	620.1	-	459	717.4	547.3	615.4	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750R3-432AXSP04	423.7	673.5	510.3	575.5	-	424.1	667.2	507.6	571.9	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD1556ZK750R3-525AXSP04	510.4	795.9	608	683	-	510.3	788	604.8	677.9	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750R3-532AXSP04	477.3	751.1	571.5	643.2	1257	477.3	744.1	568.2	638.9	1238	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD1556ZK750R3-625AXSP04	551.1	850.7	654.2	732.3	1397.1	550.8	761.7	650	726.1	1374.2	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD1556ZK750R3-632AXSP04	520.7	813.3	622.7	698.9	1346.7	521.1	805.9	619.1	693.3	1325.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9102PA177F7-425AXSP16	-	55.4	38.9	45.9	100.5	-	56.3	40.3	47	100.2	113	15.7	1-1/2"	90	10.3	1-1/2"	135	22.1	1-1/2"
EAW-VD9102PA177F7-425AXSP16	-	51.5	-	42.5	94.4	-	52.3	-	43.6	94	113	15.7	1-1/2"	90	10.3	1-1/2"	135	22.1	1-1/2"
EAW-VD9102PA177F7-525AXSP16	-	59.1	-	49	106.7	-	60	-	50.2	106.3	135	17.2	1-1/2"	108	11.3	1-1/2"	162	19.6	2"
EAW-VD9102PA177F7-532AXSP16	-	55.6	-	46	101.7	-													

EAW-VD9102PJ320P5-632AXSP16	-	80.8	57.7	67.4	143.4	-	81.7	59.4	68.5	142.5	169	15.8	2"	135	13.7	1-1/2"	203	22.3	2"
EAW-VD9102PJ320P7-425AXSP16	40.1	73.7	52.7	61.5	130.7	42.2	74.2	53.9	62.3	130	113	16.6	1-1/2"	90	10.9	1-1/2"	135	23.3	1-1/2"
EAW-VD9102PJ320P7-432AXSP16	-	67.7	48.2	56.4	121.4	38.4	68.4	49.3	57.2	120.8	113	16.6	1-1/2"	90	10.9	1-1/2"	135	23.3	1-1/2"
EAW-VD9102PJ320P7-525AXSP16	-	79.6	57.1	66.6	140.6	45.9	80.3	58.5	67.5	139.7	135	18.1	1-1/2"	108	11.9	1-1/2"	162	20.8	2"
EAW-VD9102PJ320P7-532AXSP16	-	74.1	52.8	61.8	132.4	-	74.9	54.2	62.8	131.6	135	18.1	1-1/2"	108	11.9	1-1/2"	162	20.8	2"
EAW-VD9102PJ320P7-625AXSP16	-	86.7	62.4	72.7	152.2	-	87.6	64.1	73.8	151.3	169	15.8	2"	135	13.7	1-1/2"	203	22.3	2"
EAW-VD9102PJ320P7-632AXSP16	-	82.1	58.7	68.6	145.7	-	83	60.4	69.7	144.9	169	15.8	2"	135	13.7	1-1/2"	203	22.3	2"
EAW-VD9102ZA177F7-425AXSP16	-	62.8	-	52	114.4	-	63.7	-	53.1	113.6	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA177F7-432AXSP16	-	58	-	-	107	-	59	-	49.1	106.3	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA177F7-525AXSP16	-	68.3	-	-	124	-	69.4	-	-	123	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA177F7-532AXSP16	-	64.1	-	-	117.7	-	65.3	-	-	116.9	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA177F7-625AXSP16	-	-	-	-	132.5	-	-	-	-	131.5	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA177F7-632AXSP16	-	-	-	-	128	-	-	-	-	127	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA24716-425AXSP16	-	68.7	-	56.9	124.9	-	69.7	49.9	58.1	124.1	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA24716-432AXSP16	-	63.4	-	52.4	116.6	-	64.4	-	53.6	116	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA24716-525AXSP16	-	75	-	62.2	135.7	-	76.1	-	63.6	134.9	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA24716-532AXSP16	-	70.2	-	-	128.5	-	71.4	-	-	127.8	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA24716-625AXSP16	-	81.2	-	-	146.1	-	82.6	-	-	145	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA24716-632AXSP16	-	77.2	-	-	140.6	-	78.5	-	-	139.6	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA320P5-425AXSP16	-	75.3	52.9	62.5	136.7	-	76.3	54.6	63.7	135.7	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA320P5-432AXSP16	-	69	-	57.1	126.6	-	70.1	49.8	58.3	125.9	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA320P5-525AXSP16	-	83.1	-	68.9	149.8	-	84.2	60.4	70.3	148.8	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA320P5-532AXSP16	-	77.2	-	63.8	140.9	-	78.3	-	65.2	140.1	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA320P5-625AXSP16	-	90.7	-	75.4	162.8	-	92.1	-	77.1	161.7	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA320P5-632AXSP16	-	85.6	-	-	155.6	-	87	-	-	154.5	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA320P7-425AXSP16	-	76.9	54	63.7	139.2	-	77.8	55.7	64.9	138.3	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA320P7-432AXSP16	-	70.5	49	58.2	129	-	71.4	50.8	59.4	128.4	146	14.4	2"	117	12.2	1-1/2"	176	20.2	2"
EAW-VD9102ZA320P7-525AXSP16	-	84.7	-	70.3	152.7	-	85.8	61.6	71.7	151.6	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA320P7-532AXSP16	-	78.6	-	65	143.6	-	79.9	-	66.6	142.7	180	15.5	2"	144	10.2	2"	216	21.9	2"
EAW-VD9102ZA320P7-625AXSP16	-	92.4	-	76.9	165.8	-	93.7	-	78.5	164.6	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZA320P7-632AXSP16	-	87.2	-	-	158.6	-	88.6	-	-	157.3	225	17.4	2"	180	11.4	2"	270	18.5	3"
EAW-VD9102ZJ177F7-425AXSP16	-	67.6	-	56.4	120.8	-	68.3	49.4	57.2	119.9	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ177F7-432AXSP16	-	62.6	-	52	113.2	-	63.3	-	52.9	112.1	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ177F7-525AXSP16	-	73.8	-	61.6	131	-	74.5	-	62.5	129.9	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ177F7-532AXSP16	-	69.2	-	-	124.4	-	70	-	-	123.4	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ177F7-625AXSP16	-	79.7	-	-	140.4	-	80.4	-	-	138.9	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ177F7-632AXSP16	-	76	-	-	135.6	-	76.8	-	-	134.1	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ24716-425AXSP16	-	74.3	52.9	61.9	132.3	-	74.8	54.2	62.8	131.2	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ24716-432AXSP16	-	68.5	-	56.9	123.6	-	69.1	49.8	57.9	122.6	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ24716-525AXSP16	-	81.1	-	67.8	143.9	-	81.9	-	68.8	142.7	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ24716-532AXSP16	-	76	-	63.3	136.4	-	76.7	-	64.4	135.3	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ24716-625AXSP16	-	87.9	-	-	154.8	-	88.7	-	-	153.3	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ24716-632AXSP16	-	83.6	-	-	149.1	-	84.5	-	-	147.7	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ320P5-425AXSP16	-	81.2	57.9	67.7	144.4	-	81.7	59.2	68.6	143.2	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ320P5-432AXSP16	-	74.4	52.8	61.9	134.1	-	75.2	54.2	62.9	133	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ320P5-525AXSP16	-	89.5	64.1	74.8	158.5	-	90.2	65.6	75.7	157	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ320P5-532AXSP16	-	83.2	-	69.3	149.1	-	83.9	60.7	70.4	147.8	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ320P5-625AXSP16	-	97.9	-	82	172.2	-	98.6	-	83.1	170.4	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ320P5-632AXSP16	-	92.4	-	77	164.4	-	93.2	-	78.3	163	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ320P7-425AXSP16	-	82.9	59.1	69.1	147.4	-	83.4	60.4	69.9	146.2	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ320P7-432AXSP16	-	76	53.9	63.2	136.7	-	76.6	55.2	64.1	135.7	146	15.3	2"	117	12.8	1-1/2"	176	21.5	2"
EAW-VD9102ZJ320P7-525AXSP16	-	91.3	65.4	76.4	161.6	-	91.9	67	77.2	160.3	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ320P7-532AXSP16	-	84.9	60.4	70.8	152.1	-	85.7	62	71.9	150.9	180	16.4	2"	144	10.8	2"	216	23.1	2"
EAW-VD9102ZJ320P7-625AXSP16	-	99.8	-	83.7	175.6	-	100.7	-	84.8	173.9	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9102ZJ320P7-632AXSP16	-	94.2	-	78.6	167.8	-	95.1	-	79.9	166.2	225	18.3	2"	180	12	2"	270	19.7	3"
EAW-VD9104PA177F7-425AXSP16	77.4	124	93.5	106	-	78	123.8	93.8	105.8	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD9104PA177F7-432AXSP16	71.6	116	87.1	98.8	-	72.2	115.4	87.1	98.7	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD9104PA177F7-525AXSP16	83.4	132.8	100.7	113.6	223.6	84.1	132.5	100.8	113.5	221.4	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD9104PA177F7-532AXSP16	78	125.9	95.1	107.6	213.6	78.9	125.4	95.1	107.3	211.5	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD9104PA177F7-625AXSP16	90.6	143	109.2	122.9	237.7	91.4	142.5	109.3	122.7	235.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD9104PA177F7-632AXSP16	86.4	138	104.8	118.2	231.4	87.2	137.6	104.8	118	229	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD9104PA24716-425AXSP16	83.6	134.4	101.4	114.8	-	84.3	134.1	101.6	114.7	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD9104PA24716-432AXSP16	77.3	125.2	94	106.8	-	77.9	124.8	94.2	106.6	-	113	23.6	1-1/2"	90	15.6	1-1/2"	135	33.1	1-1/2"
EAW-VD9104PA24716-525AXSP16	90.7	144.5	109.3	123.6	-	91.4	144	109.5	123.3	-	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD9104PA24716-532AXSP16	84.6	136.3	102.7	116.4	-	85.5	135.9	102.9	116.3	-	135	25.1	1-1/2"	108	16.6	1-1/2"	162	30.7	2"
EAW-VD9104PA24716-625AXSP16	99	156.3	119.1	134.1	260.3	99.9	155.8	119.2	133.9	257.9	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD9104PA24716-632AXSP16	93.9	150.1	113.9	128.5	252.3	94.9	149.6	114	128.3	250.1	169	22.9	2"	135	18.4	1-1/2"	203	32.1	2"
EAW-VD9104PA320P5-425AXSP16	91.6	148	111.3	126.2	-	92.3	147.6	111.4	125.8	-	113	23.6							

EAW-VD9104P3J20P7-625AXSP16	121.7	190.5	145.4	163.6	-	122.4	189.6	145.2	163	-	169	24.6	2"	135	19.5	1-1/2"	203	34.6	2"
EAW-VD9104P3J20P7-632AXSP16	114.7	181.1	137.8	155.3	-	115.3	180.3	137.5	154.6	-	169	24.6	2"	135	19.5	1-1/2"	203	34.6	2"
EAW-VD9104Z177F7-425AXSP16	88.1	141.6	106.9	121.1	240	88.7	140.7	106.9	120.5	236.9	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z177F7-432AXSP16	81.1	131.6	99.2	112.4	224.7	81.7	131	99	111.9	222	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z177F7-525AXSP16	97	154.7	117.6	132.7	259.4	97.7	153.8	117.4	131.9	256.1	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z177F7-532AXSP16	90.6	146.1	110.4	125.1	247.1	91.2	145.4	110.1	124.4	243.9	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z177F7-625AXSP16	106.2	168	128	144.1	277.7	106.9	166.6	127.7	143.3	273.8	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z177F7-632AXSP16	100.5	161.1	121.9	137.9	266.7	101.4	160	121.7	137.2	265.1	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z24716-425AXSP16	96.1	154.2	116.3	131.8	-	96.7	153.5	116.3	131.1	-	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z24716-432AXSP16	88.3	143.3	107.7	122.1	-	88.9	142.5	107.5	121.6	242.1	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z24716-525AXSP16	106.2	169.1	128.4	144.8	284.3	106.7	168.3	128.2	144.1	280.9	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z24716-532AXSP16	98.7	159.3	120.3	136	269.9	99.6	158.4	120.2	135.5	266.7	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z24716-625AXSP16	116.4	184.1	140.2	158.1	305.4	117.2	182.8	140.1	157.2	301.4	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z24716-632AXSP16	110	176	133.4	150.9	294.8	110.8	175	133.1	150.2	290.7	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z320P5-425AXSP16	104.6	168.3	126.9	143.7	-	105.3	167.4	126.8	143.2	-	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z320P5-432AXSP16	95.8	155.4	116.7	132.4	-	96.4	154.5	116.5	131.9	-	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z320P5-525AXSP16	116.9	186.3	141.1	159.4	-	117.7	185.3	140.9	158.5	-	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z320P5-532AXSP16	108	174.2	131.5	148.7	295.9	108.8	173.2	131.1	148	292.2	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z320P5-625AXSP16	129.5	204.6	156	175.4	340.8	130.2	203.1	155.6	174.5	336	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z320P5-632AXSP16	121.3	193.9	147.1	166.1	325.9	122.2	192.8	146.8	165.3	321.5	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z320P7-425AXSP16	106.6	171.6	129.3	146.5	-	107.1	170.5	129	145.8	-	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z320P7-432AXSP16	97.6	158.2	118.8	134.9	-	98.3	157.5	118.7	134.3	-	146	22.3	2"	117	17.4	1-1/2"	176	31.3	2"
EAW-VD9104Z320P7-525AXSP16	119	189.5	143.6	162.3	-	119.6	188.6	143.3	161.5	-	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z320P7-532AXSP16	110.2	177.3	133.7	151.5	-	110.8	176.3	133.6	150.9	297.7	180	23.4	2"	144	15.5	2"	216	32.9	2"
EAW-VD9104Z320P7-625AXSP16	131.7	208.2	158.7	178.4	346.9	132.5	206.7	158.3	177.6	342.2	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z320P7-632AXSP16	123.4	197.5	150	169.2	332.1	124.4	196.2	149.5	168.2	327.8	225	25.3	2"	180	16.7	2"	270	29.5	3"
EAW-VD9104Z177F7-425AXSP16	94.4	149.7	113.6	128.1	-	94.6	148.6	113	127.3	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z177F7-432AXSP16	86.9	139.3	105.4	119.1	236.6	87.2	138.4	105	118.3	233.1	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z177F7-525AXSP16	104.1	163.9	125	140.7	273.1	104.4	162.5	124.5	139.6	268.8	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z177F7-532AXSP16	97.2	154.6	117.4	132.6	259.5	97.5	153.3	116.9	131.4	255.8	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z177F7-625AXSP16	113.9	177.6	136.2	153	291.8	114.2	176	135.5	151.7	287.4	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z177F7-632AXSP16	108	170.4	129.9	146.3	282.5	108.3	168.7	129.2	145.1	278	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z24716-425AXSP16	103	163.7	124	139.9	-	103.2	162.3	123.4	139.2	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z24716-432AXSP16	94.8	151.7	114.5	129.6	-	95.1	150.7	114.2	128.9	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z24716-525AXSP16	114.1	179.6	136.7	153.8	299.9	114.2	178	136.2	152.8	295.6	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z24716-532AXSP16	106.2	168.9	128.3	144.8	284.5	106.5	167.7	127.6	143.7	280.7	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z24716-625AXSP16	125.1	195.2	149.9	167.9	322	125.5	193.5	149	166.8	316.9	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z24716-632AXSP16	118.3	186.6	142.5	160.2	310.6	118.7	185.1	141.7	159.1	306	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z320P5-425AXSP16	111.9	178.2	134.7	152.3	-	111.9	177	134.3	151.5	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z320P5-432AXSP16	102.5	164.5	123.9	140.4	-	102.8	163.4	123.5	139.4	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z320P5-525AXSP16	125.2	197.1	150	169	-	125.3	195.5	149.3	167.8	-	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z320P5-532AXSP16	115.8	184.2	139.6	157.6	-	116.1	182.9	139.1	156.6	-	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z320P5-625AXSP16	138.7	216.3	165.7	186	358.2	138.9	214.3	164.9	184.5	352.6	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z320P5-632AXSP16	130.1	205.2	156.6	176.1	343	130.5	203.7	155.8	174.7	337.5	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z320P7-425AXSP16	114	181.8	137.5	155.3	-	114.1	180.4	137	154.5	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z320P7-432AXSP16	104.4	167.8	126.4	143.1	-	104.7	166.7	125.9	142.1	-	146	24.1	2"	117	18.6	1-1/2"	176	33.8	2"
EAW-VD9104Z320P7-525AXSP16	127.4	201.2	152.7	172.4	-	127.6	199.6	152.1	171	-	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z320P7-532AXSP16	118.1	187.9	142.2	160.9	-	118.3	186.6	141.8	159.7	-	180	25.2	2"	144	16.6	2"	216	35.4	2"
EAW-VD9104Z320P7-625AXSP16	141.3	220.6	168.8	189.6	365.4	141.6	218.6	167.9	188.1	359.9	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9104Z320P7-632AXSP16	132.6	209.4	159.4	179.6	349.7	132.9	207.6	158.6	178.3	344.7	225	27.1	2"	180	17.8	2"	270	32	3"
EAW-VD9106PA177F7-425AXSP12	116.1	184.8	139.8	158.1	-	116.6	184.2	139.7	157.6	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD9106PA177F7-432AXSP12	107.4	172.3	129.9	147.2	-	108	171.5	129.9	146.8	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD9106PA177F7-525AXSP12	127.5	201	152.8	172.1	-	128.1	200.2	152.7	171.5	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD9106PA177F7-532AXSP12	119.8	190.4	144.2	162.8	-	120.6	189.6	144.2	162.4	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD9106PA177F7-625AXSP12	139	216.5	165.9	186	357.8	139.8	215.5	165.6	185.5	353.9	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD9106PA177F7-632AXSP12	138	213.3	163.6	183.3	-	138	211.5	162.8	182.2	-	169	30.8	2"	135	23.6	1-1/2"	203	43.2	2"
EAW-VD9106PA24716-425AXSP12	125.4	200.2	151.4	171.3	-	126	199.8	151.2	170.8	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD9106PA24716-432AXSP12	115.8	186.4	140.2	159	-	116.4	185.8	140.2	158.5	-	146	23.1	2"	117	17.7	1-1/2"	176	32.4	2"
EAW-VD9106PA24716-525AXSP12	138.2	218.4	165.9	187.1	-	139.1	217.6	165.9	186.7	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD9106PA24716-532AXSP12	129.5	206.2	155.8	176.2	-	130.3	205.3	156	175.9	-	180	24.1	2"	144	15.9	2"	216	33.9	2"
EAW-VD9106PA24716-625AXSP12	151.8	236.3	180.8	203.2	-	152.6	235.3	180.6	202.5	-	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD9106PA24716-632AXSP12	144.2	227.1	172.8	194.8	-	144.9	226	172.6	194.2	376.1	225	25.9	2"	180	17.1	2"	270	30.7	3"
EAW-VD9106PA320P5-425AXSP08	127.7	213.9	159	181.5	371.4	130.4	214.3	160.2	182.3	369	225	18.9	2"	180	12.4	2"	270	20.9	3"
EAW-VD9106PA320P5-432AXSP12	126	203.4	152.8	173.4	-</														

EAW-VD91062A177F7-532AXSP16	145.1	226	172.5	193.8	-	144.6	223.7	171.3	192	-	180	31.3	2"	144	20.7	2"	216	44	2"
EAW-VD91062A177F7-625AXSP16	170	259	200	223.5	-	169.3	255.8	198.3	221.2	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD91062A177F7-632AXSP16	161.7	248.6	191.2	214.1	-	161.1	245.8	189.6	212	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD91062A24716-425AXSP12	150.1	238.7	180.7	204.4	-	150.6	237	180.2	203.2	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD91062A24716-432AXSP12	138.7	222	167.5	189.6	-	139.2	220.7	167.3	188.7	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD91062A24716-525AXSP12	165.6	260	198.2	223	-	166	258.3	197.6	221.8	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD91062A24716-532AXSP12	154.5	245.1	186	210	413	154.9	247.7	185.6	208.7	407.9	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD91062A24716-625AXSP12	179.8	279.7	214.6	240.8	461.9	180.2	273.8	213.8	239.3	455.8	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD91062A24716-632AXSP16	176.2	271.8	208.5	233.8	-	175.5	269.1	207	231.6	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD91062A320P5-425AXSP12	163.6	260.8	197.4	222.8	-	164.2	258.8	196.7	221.8	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD91062A320P5-432AXSP12	150.1	241.1	181.6	205.8	-	150.5	239.2	181.1	204.4	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD91062A320P5-525AXSP12	181.9	286.7	218.1	245.7	-	182.3	284.6	216.9	244.2	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD91062A320P5-532AXSP12	168.7	268.3	203.1	229.8	-	169.1	266.6	202.7	228.2	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD91062A320P5-625AXSP12	199.7	311	238.2	267.2	-	200.1	308.6	237.1	265.4	-	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD91062A320P5-632AXSP16	193.5	299.8	229.6	257.7	-	192.7	296.6	227.8	255.2	-	225	33.2	2"	180	21.9	2"	270	40.6	3"
EAW-VD91062A320P7-425AXSP12	166.7	265.6	200.8	227.1	-	167	264.1	200.2	225.9	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD91062A320P7-432AXSP12	152.8	245.7	185	209.4	-	153.4	243.8	184.5	208.3	-	203	25.2	2"	162	16.6	2"	244	30.5	3"
EAW-VD91062A320P7-525AXSP12	184.8	291.7	221.7	250.2	-	185.4	289.7	221	248.5	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD91062A320P7-532AXSP12	171.8	273.1	206.9	233.7	-	172.3	271.5	206.2	232.3	-	248	22.2	3"	198	18	2"	298	31.1	3"
EAW-VD91062A320P7-625AXSP12	203.4	316.6	242.3	271.9	-	203.5	314.2	241.3	270.2	-	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD91062A320P7-632AXSP12	190.9	300.7	229	257.7	502.8	191.3	298.5	228.2	256.2	496.3	304	22.8	3"	244	15.1	3"	365	32	3"
EAW-VD91062J177F7-425AXSP12	147.3	231.3	176.1	198.2	-	147	229.1	175	196.6	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J177F7-432AXSP12	136.2	215.4	163.5	184.5	-	136.2	213.6	162.5	183.2	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J177F7-525AXSP12	161.9	251.4	192.7	216.3	-	161.7	249	191.2	214.2	409.8	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J177F7-532AXSP12	151.4	237.8	181.4	204	396.7	151.2	235.4	180.2	202.1	391	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J177F7-625AXSP12	175.3	269.8	208.2	232.5	441.3	175.1	266.9	206.5	230.5	434	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD91062J177F7-632AXSP16	171.7	262.1	202.3	226	-	170.5	258.8	200.3	223.4	-	225	35.8	2"	180	23.6	2"	270	44.3	3"
EAW-VD91062J24716-425AXSP12	160.3	252.7	192.3	216.8	-	160.5	250.5	191	214.8	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J24716-432AXSP12	148	234.9	177.9	201.1	-	148.2	233.1	177	199.5	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J24716-525AXSP12	176.7	275.5	210.6	236.7	-	176.8	273	209.3	234.7	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J24716-532AXSP12	165.3	259.7	198	223	-	165.4	257.8	196.6	221.2	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J24716-625AXSP12	192.6	296.5	228.3	255.6	487	192.3	293.5	226.6	253.2	479.2	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD91062J24716-632AXSP12	182.2	283.8	217.6	243.9	470	182.2	281	216.1	242	462.9	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD91062J320P5-425AXSP12	174.4	275.4	209.2	235.8	-	174.3	272.9	208.1	234	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J320P5-432AXSP12	160.1	254.5	192.8	217.8	-	160	252.6	191.7	216	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J320P5-525AXSP12	193.8	303.2	231.3	260.3	-	193.6	300.1	229.7	257.9	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J320P5-532AXSP12	179.9	283.5	215.8	242.9	-	179.9	280.8	214.2	240.9	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J320P5-625AXSP12	213	328.8	252.8	282.9	-	212.7	325.6	250.8	280.5	-	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD91062J320P5-632AXSP12	200.2	312.2	239	268.1	-	200.1	309.3	237.2	266	-	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD91062J320P7-425AXSP08	163.8	269.9	202.4	229.9	463.2	163.8	269.9	202.8	229.7	457.8	304	17.1	3"	244	11.3	3"	365	24	3"
EAW-VD91062J320P7-432AXSP12	163	259.7	196.5	222	-	163.1	257.8	195.5	220.3	-	203	27.2	2"	162	17.9	2"	244	33.3	3"
EAW-VD91062J320P7-525AXSP12	197.3	308.9	235.5	265.1	-	197.2	305.9	234.4	262.8	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J320P7-532AXSP12	183.2	289.1	219.9	247.6	-	183.4	286.6	218.4	245.7	-	248	24.1	3"	198	19.3	2"	298	33.9	3"
EAW-VD91062J320P7-625AXSP12	217.1	335.3	257.3	288.4	-	216.8	331.8	255.8	286.1	-	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD91062J320P7-632AXSP12	204.1	318.1	243.3	273.5	-	204.1	313.5	241.6	271	-	304	24.8	3"	244	16.4	3"	365	34.7	3"
EAW-VD9108PA177F7-425AXSP08	153.9	247.2	186.4	210.8	-	155.1	246.4	186.6	210.8	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA177F7-432AXSP08	142.3	230.6	173.2	196.5	-	143.6	230	173.4	196.2	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA177F7-525AXSP08	169.7	270.4	205	231.6	454.4	171.4	269.6	205.5	231.2	449.8	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD9108PA177F7-532AXSP08	159.4	256.7	194	219.3	434.8	160.7	255.7	194	219.1	430.2	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD9108PA177F7-625AXSP12	192.2	293.9	226.6	253.4	-	192	292.1	225.8	251.7	-	225	31.8	2"	180	21	2"	270	39	3"
EAW-VD9108PA177F7-632AXSP08	171.9	274.9	208.6	235.7	461	173.5	274	208.6	235.2	456.3	338	20	3"	270	13.2	3"	406	28.2	3"
EAW-VD9108PA24716-425AXSP08	166.3	267.9	201.5	228.3	-	167.7	267.3	202	228.1	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA24716-432AXSP08	153.7	249	186.9	212.4	-	155	248.7	187.4	212	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA24716-525AXSP08	185	294.3	222.7	251.6	-	186.4	293.6	223.1	251.3	-	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD9108PA24716-532AXSP08	172.6	278.2	209.7	237.5	-	174.3	277.3	209.9	237	468.2	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD9108PA24716-625AXSP08	197.1	311.3	237.2	267.1	519.3	198.9	310.4	237.7	266.7	514.5	338	20	3"	270	13.2	3"	406	28.2	3"
EAW-VD9108PA24716-632AXSP08	186.8	299.2	226.7	256.1	503.2	188.8	297.9	227.2	255.7	498.1	338	20	3"	270	13.2	3"	406	28.2	3"
EAW-VD9108PA320P5-425AXSP08	182.1	294.3	221.4	251	-	183.7	293.6	221.6	250.7	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA320P5-432AXSP08	167.3	272	203.8	231.7	-	168.8	271.2	204.1	231.2	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA320P5-525AXSP08	204.5	326.4	246.7	279.2	-	206.2	325.7	247.2	278.5	-	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD9108PA320P5-532AXSP08	190.2	306.3	230.6	261.2	-	192	305.2	230.8	261.1	-	282	19.4	3"	225	16.8	2"	338	27.2	3"
EAW-VD9108PA320P5-625AXSP08	220.2	348.2	264.7	298.5	-	222.4	347.3	265.4	298.1	-	338	20	3"	270	13.2	3"	406	28.2	3"
EAW-VD9108PA320P5-632AXSP08	207.4	331.5	250.8	283.5	559.8	209.3	330.6	251.2	283.1	554.1	338	20	3"	270	13.2	3"	406	28.2	3"
EAW-VD9108PA320P7-425AXSP08	184.8	298.8	224.5	254.7	-	186.5	298.1	224.9	254.5	-	225	22.8	2"	180	15	2"	270	26.4	3"
EAW-VD9108PA320P7-432AXSP08	169.7	276	206.8	234.9	-	171.2	275.5	207.1	234.7	-	2								

EAW-VD91082A24716-525AXSP08	214.9	342.7	260.1	293.2	575.5	216.3	340.5	259.8	292.1	567.7	372	20.6	3"	298	13.6	3"	446	28.9	3"
EAW-VD91082A24716-532AXSP12	213.8	333.5	254.9	286.1	-	213.1	330.4	253	283.7	-	248	28.1	3"	198	21.9	2"	298	39.4	3"
EAW-VD91082A24716-625AXSP12	248.9	380.2	293.4	328	-	248.2	376.5	291.3	324.7	-	304	28.7	3"	244	19	3"	365	40.3	3"
EAW-VD91082A24716-632AXSP12	236	364	279.7	313.5	-	235.4	360.2	277.6	310.6	-	304	28.7	3"	244	19	3"	365	40.3	3"
EAW-VD91082A320P5-425AXSP08	213.6	343.1	258.7	292.8	-	214.7	341.1	258.4	291.6	-	304	19.7	3"	244	13	3"	365	27.7	3"
EAW-VD91082A320P5-432AXSP08	195.5	316.7	238.1	270.2	-	196.8	315.4	237.8	268.9	-	304	19.7	3"	244	13	3"	365	27.7	3"
EAW-VD91082A320P5-525AXSP08	237.1	377.1	285.9	322.9	-	238.2	375.1	285.5	321.6	-	372	20.6	3"	298	13.6	3"	446	28.9	3"
EAW-VD91082A320P5-532AXSP08	219.4	353.1	266.4	301.6	599.7	220.5	351	266	300.2	592.1	372	20.6	3"	298	13.6	3"	446	28.9	3"
EAW-VD91082A320P5-625AXSP08	257.8	407.5	310.7	349.8	679	259.3	405.1	309.9	348	670.3	451	21.9	3"	361	14.4	3"	541	26.9	4"
EAW-VD91082A320P5-632AXSP12	259.6	401.5	308	345.2	-	258.5	397.1	305.6	341.8	-	304	28.7	3"	244	19	3"	365	40.3	3"
EAW-VD91082A320P7-425AXSP08	217.3	349.3	263.1	298.5	-	218.4	347.5	263	296.9	-	304	19.7	3"	244	13	3"	365	27.7	3"
EAW-VD91082A320P7-432AXSP08	199.3	322.6	242.5	275.1	-	200.5	321.5	242.2	273.9	-	304	19.7	3"	244	13	3"	365	27.7	3"
EAW-VD91082A320P7-525AXSP08	241.3	384.2	291.1	328.9	-	242.6	381.8	290.4	327.2	-	372	20.6	3"	298	13.6	3"	446	28.9	3"
EAW-VD91082A320P7-532AXSP08	223.4	359.3	271.4	307.3	610.8	224.6	357.9	271	306	603.3	372	20.6	3"	298	13.6	3"	446	28.9	3"
EAW-VD91082A320P7-625AXSP08	262.1	414.7	316	355.8	691.3	263.7	412.3	315.3	354.2	682.7	451	21.9	3"	361	14.4	3"	541	26.9	4"
EAW-VD91082A320P7-632AXSP08	245.6	393.4	298.5	336.7	661.5	247.6	391.2	298	335.4	653.1	451	21.9	3"	361	14.4	3"	541	26.9	4"
EAW-VD91082J177F7-425AXSP08	192.2	304.6	231.2	260.9	-	192.6	302.2	230.3	259.2	505.2	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J177F7-432AXSP08	177.1	283.9	214.8	243	481.2	177.9	282	213.9	241.2	474.7	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J177F7-525AXSP08	210.8	331.5	253.1	284.7	551.7	211.1	328.9	252	282.4	543.7	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J177F7-532AXSP08	196.7	313.4	237.9	268.5	525.4	197.3	310.7	236.8	266.6	517.8	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J177F7-625AXSP12	241.8	365.4	283.5	316.1	-	240.4	361	280.4	312.1	-	304	31.3	3"	244	20.7	3"	365	43.9	3"
EAW-VD91082J177F7-632AXSP12	229.9	351.2	270.8	303	-	228.7	346.8	268.2	299	-	304	31.3	3"	244	20.7	3"	365	43.9	3"
EAW-VD91082J24716-425AXSP08	209.8	333.2	252.4	285.2	-	210.2	330.9	251.6	283.1	-	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J24716-432AXSP08	193.2	309.4	233.6	264.7	-	193.7	307.1	232.9	263.1	-	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J24716-525AXSP08	230.8	363.3	276.9	311.8	606.1	231.4	360.5	275.7	309.8	598	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J24716-532AXSP08	215	342.6	260.1	293.4	576.2	216	340.1	259.2	291.2	568.5	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J24716-625AXSP08	249.1	389.4	298.5	334.8	641.8	250	386	296.9	332.3	632.3	451	23.6	3"	361	15.6	3"	541	29.4	4"
EAW-VD91082J24716-632AXSP12	251.2	385.1	296.6	331.7	-	249.9	380.1	293.6	328.2	-	304	31.3	3"	244	20.7	3"	365	43.9	3"
EAW-VD91082J320P5-425AXSP08	227.7	363	274.9	310.6	-	228.5	360.4	273.6	308.2	-	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J320P5-432AXSP08	209.2	335.1	253	286.5	-	209.7	333.2	252.2	284.7	-	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J320P5-525AXSP08	253.8	399.5	304	342.3	-	253.9	396.1	302.5	339.7	-	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J320P5-532AXSP08	235	373.8	283.2	320	-	235.6	371	282.1	317.4	-	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J320P5-625AXSP08	276.2	431.6	329.9	370.4	714.7	276.7	427.5	328.3	367.9	703.6	451	23.6	3"	361	15.6	3"	541	29.4	4"
EAW-VD91082J320P5-632AXSP08	258.8	409.3	311.7	350.6	683.3	259.7	405.6	310.1	348.4	673.4	451	23.6	3"	361	15.6	3"	541	29.4	4"
EAW-VD91082J320P7-425AXSP08	232.5	370.4	280.2	316.7	-	233	367.3	279	314.5	-	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J320P7-432AXSP08	213.3	341.8	257.8	292	-	213.9	339.4	257.1	290.4	-	304	21.5	3"	244	14.2	3"	365	30.1	3"
EAW-VD91082J320P7-525AXSP08	258.3	407.1	309.5	349.1	-	258.6	403.8	308.1	346.7	-	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J320P7-532AXSP08	239.3	381.2	288.5	326.2	-	240.2	378	287.7	323.8	-	372	22.4	3"	298	14.8	3"	446	31.4	3"
EAW-VD91082J320P7-625AXSP08	281.4	439.4	336.2	377.6	729.1	282	435.6	334.8	374.7	718.1	451	23.6	3"	361	15.6	3"	541	29.4	4"
EAW-VD91082J320P7-632AXSP08	263.8	417	317.4	357.6	697.5	264.9	413.4	316.3	355	686.7	451	23.6	3"	361	15.6	3"	541	29.4	4"
EAW-VD9110PA177F7-425AXSP08	198.9	314.8	238.7	269.2	-	199.5	313.1	237.9	268.2	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD9110PA177F7-432AXSP08	184.2	293.7	222	250.9	-	184.7	292.2	221.4	250	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD9110PA177F7-525AXSP08	220.1	344	262.6	295.4	-	220.6	342.3	261.8	293.8	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD9110PA177F7-532AXSP08	207.2	326.6	248.1	279.7	-	207.9	324.6	247.5	278.4	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD9110PA177F7-625AXSP08	234.7	362.7	278.5	312.1	-	235.3	360.5	277.6	310.4	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA177F7-632AXSP08	224.3	350	267.3	300.5	-	225.1	347.8	266.9	298.9	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA24716-625AXSP06	201.2	326.1	245.1	277.9	-	203.5	326.1	245.7	278.4	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD9110PA24716-432AXSP08	198.6	317.3	239.8	271.1	-	199.2	316.1	239.2	270.3	-	225	26.8	2"	180	17.6	2"	270	32	3"
EAW-VD9110PA24716-525AXSP08	238.5	374.5	285.4	321	-	239.3	372.4	284.8	319.5	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD9110PA24716-532AXSP08	223.8	354	268.5	303.1	-	224.5	352.2	268.1	302	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD9110PA24716-625AXSP08	255.6	395.9	303.6	340.6	-	256.6	394.2	302.8	339	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA24716-632AXSP08	243.2	380.7	290.3	326.7	-	243.9	378.3	289.5	325.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA320P5-425AXSP06	220.5	358.5	268.8	305.3	-	222.9	357.8	269.5	305.6	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD9110PA320P5-432AXSP06	202.3	331	247.4	281.4	-	204.3	330.4	248	281.3	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD9110PA320P5-525AXSP06	250	402.2	303	343.1	-	252.7	401.5	303.7	343	-	372	19	3"	298	12.5	3"	446	26.7	3"
EAW-VD9110PA320P5-532AXSP08	245.9	390.2	295.5	333.7	-	246.7	388	294.5	332.3	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD9110PA320P5-625AXSP08	284.7	443.2	339.1	380.9	-	285.4	440.7	338.3	379.2	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA320P5-632AXSP08	268.6	422.1	321.6	361.9	-	269.4	419.5	320.8	360.2	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA320P7-425AXSP06	223.7	363.8	272.8	310	-	226	363.2	273.4	310.1	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD9110PA320P7-432AXSP06	205.2	335.8	250.8	285.6	-	207.4	335.4	251.6	285.5	-	293	18	3"	234	16.2	2"	352	25.2	3"
EAW-VD9110PA320P7-525AXSP06	253.9	408.3	307.4	348.2	-	256.7	407.5	308.6	348	-	372	19	3"	298	12.5	3"	446	26.7	3"
EAW-VD9110PA320P7-532AXSP08	242.2	395.8	299.6	338.4	-	250.2	393.9	299.4	337.2	-	282	23.3	3"	225	19.4	2"	338	32.7	3"
EAW-VD9110PA320P7-625AXSP08	289.2	450.5	344.5	387.1	-	289.8	447.7	343.5	385.1	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PA320P7-632AXSP08	272.4	428.4	326.2	367.3	-	273.3	425.9	325.4	365.5	-	338	24	3"	270	15.8	3"	406	33.7	3"
EAW-VD9110PJ177F7-425AXSP06	201.2	322.3	243.6	275.5	-	202.8	321.3												

EAW-VD9110ZA320P5-432AXSP08	252.9	403.4	304.9	345.1	-	253.2	400.1	303.4	342.7	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD9110ZA320P5-525AXSP08	306.3	480.6	365.8	412	-	306.4	476.4	363.9	408.9	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD9110ZA320P5-532AXSP08	284.4	449.4	341.6	384.9	-	284.5	445.8	339.6	382.3	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD9110ZA320P5-625AXSP08	334.3	518.4	397.6	446	-	334.4	513.7	395.2	442.4	-	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD9110ZA320P5-632AXSP08	314.7	491.9	375.5	421.8	-	314.6	487.4	373.3	418.4	-	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD9110ZA320P7-425AXSP06	267.5	432.8	325.1	369	-	269.8	430.7	325.7	367.8	-	406	19.6	3"	325	12.9	3"	487	27.5	3"
EAW-VD9110ZA320P7-432AXSP08	257.5	411	310.6	351.4	-	257.8	407.9	309.3	349.2	-	304	23.7	3"	244	15.6	3"	365	33.2	3"
EAW-VD9110ZA320P7-525AXSP08	311.8	489	372.5	419.7	-	311.6	485	370.8	416.1	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD9110ZA320P7-532AXSP08	289.6	458.1	347.4	392.3	-	289.9	453.9	346.1	389.1	-	372	24.6	3"	298	16.2	3"	446	34.5	3"
EAW-VD9110ZA320P7-625AXSP08	340	527.6	404.5	453.8	-	340.2	523	402.2	450.3	-	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD9110ZA320P7-632AXSP08	319.8	500.4	381.6	429.5	-	319.8	496.1	379.7	426.3	-	451	25.8	3"	361	17	3"	541	32.4	4"
EAW-VD9110Z117F7-425AXSP08	247.6	387.2	295.5	332	-	247	382.9	293.2	329.2	-	304	25.9	3"	244	17.1	3"	365	36.3	3"
EAW-VD9110Z117F7-432AXSP08	229.2	360.8	274.1	309.2	-	228.7	357.1	272.3	306.3	-	304	25.9	3"	244	17.1	3"	365	36.3	3"
EAW-VD9110Z117F7-525AXSP08	272.7	421.2	323.1	362	-	271.5	416.2	320.6	358.5	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z117F7-532AXSP08	255.3	398.1	304.3	341.5	-	254.6	393.5	301.8	338.4	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z117F7-625AXSP08	294.6	449.6	347	387.6	733.8	293.4	444.2	344.2	383.7	720.9	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z117F7-632AXSP08	279.1	431.1	331.3	371	709.8	278.1	426.3	328.7	367.2	698.4	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z24716-425AXSP08	270.1	423.1	322.7	363.2	-	269.3	419.4	320	359.8	-	304	25.9	3"	244	17.1	3"	365	36.3	3"
EAW-VD9110Z24716-432AXSP08	249.1	393.6	298.9	337	-	248.9	389.9	296.7	334.2	-	304	25.9	3"	244	17.1	3"	365	36.3	3"
EAW-VD9110Z24716-525AXSP08	297.4	461.2	353.7	396.8	-	297	456.8	351	392.9	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z24716-532AXSP08	278.5	434.9	331.7	373.4	-	277.5	430.9	329.9	369.9	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z24716-625AXSP08	322.4	493.6	380.5	425.9	-	321.4	488.6	377.7	421.4	-	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z24716-632AXSP08	305.6	472.3	362.6	406.4	-	304.5	467	359.6	402.2	-	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z320P5-425AXSP06	281.3	450	339.8	384.1	-	281.9	446.9	338.9	382	-	406	21.2	3"	325	14	3"	487	29.8	3"
EAW-VD9110Z320P5-432AXSP08	269.3	426.5	323.2	365	-	268.6	422.4	320.8	361.3	-	304	25.9	3"	244	17.1	3"	365	36.3	3"
EAW-VD9110Z320P5-525AXSP08	326.3	507.5	388	435.8	-	325.2	502.2	385.3	431.8	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z320P5-532AXSP08	302.5	474.8	361.5	407.5	-	302	470.2	358.8	403.4	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z320P5-625AXSP08	356.1	547.3	421.3	471.5	-	354.9	541.3	418	466.8	-	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z320P5-632AXSP08	334.7	519.6	397.7	446.2	-	334	514.1	394.7	442	-	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z320P7-425AXSP06	286.6	459.1	346.4	391.7	-	288	456.2	345.6	389.7	-	406	21.2	3"	325	14	3"	487	29.8	3"
EAW-VD9110Z320P7-432AXSP06	262.5	424.1	319	361.4	-	264	421.2	318.3	359.5	-	406	21.2	3"	325	14	3"	487	29.8	3"
EAW-VD9110Z320P7-525AXSP06	322.3	511.1	388.1	437.8	-	323.8	507	387	434.7	845.9	507	23	3"	406	15.2	3"	609	27.6	4"
EAW-VD9110Z320P7-532AXSP08	308.7	484.2	369	415.4	-	307.8	479.1	366.5	411.5	-	372	26.8	3"	298	17.7	3"	446	37.6	3"
EAW-VD9110Z320P7-625AXSP08	362.9	558	429.4	480.6	-	361.4	552.3	425.7	475.5	-	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9110Z320P7-632AXSP08	340.7	529.4	405.5	455.2	-	340.1	524.1	402.1	451	-	451	28	3"	361	18.5	3"	541	35.5	4"
EAW-VD9112P117F7-425AXSP06	230.4	367.7	278	314.5	-	231.8	366	277.8	313.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD9112P117F7-432AXSP06	213.2	342.7	258.2	292.4	-	214.4	341.2	258	291.4	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD9112P117F7-525AXSP06	258	406.2	309.1	348.5	-	259.6	404.4	308.8	347.3	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P117F7-532AXSP06	242.7	385.1	292	329.5	-	243.8	383.5	292	328.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P117F7-625AXSP08	287.4	440.3	339.4	379.1	-	288	437	337.7	377	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD9112P117F7-632AXSP08	274.7	424.7	325.8	365.5	-	274.7	421.4	324.1	362.9	-	338	27.9	3"	270	18.5	3"	406	39.2	3"
EAW-VD9112P24716-425AXSP06	248.9	398.4	300.5	339.9	-	250.3	396.9	300.6	339.1	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD9112P24716-432AXSP06	229.8	369.9	278.5	315.7	-	231.2	368.7	278.7	314.8	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD9112P24716-525AXSP06	279.9	442.1	335.8	378.5	-	281.5	440.4	335.7	377.5	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P24716-532AXSP06	262	417.2	315.8	356.8	-	264	415.9	316.1	356.2	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P24716-625AXSP06	301.6	470.7	359.5	404.1	-	303.3	468.7	359.7	402.8	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD9112P24716-632AXSP06	286.6	451.5	343.9	387.2	-	287.9	450.1	343.6	385.9	749.2	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD9112P320P5-425AXSP04	252.1	423.7	314.7	359.3	736.7	257.6	424.6	317.1	361	730.8	451	16.7	3"	361	11	3"	541	19.8	4"
EAW-VD9112P320P5-432AXSP04	250.1	403.8	303.6	344.5	-	251.5	402.5	303.5	343.5	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD9112P320P5-525AXSP06	309	490.4	372.1	419.5	-	310.9	488.6	371.4	418.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P320P5-532AXSP06	287.6	459.4	347.3	393.2	-	289.2	457.8	346.9	391.7	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P320P5-625AXSP06	335.7	525.9	401.4	451.8	-	337.8	523.8	401.1	450.4	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD9112P320P5-632AXSP06	316.7	501.1	380.1	428.7	-	318.4	499	379.9	427.4	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD9112P320P7-425AXSP04	256	430	319	364.4	748.3	261.7	431	322	366.1	742.6	451	16.7	3"	361	11	3"	541	19.8	4"
EAW-VD9112P320P7-432AXSP06	253.7	409.7	308.1	349.3	-	255.3	408.3	307.8	348.6	-	293	20.9	3"	234	18.1	2"	352	29.4	3"
EAW-VD9112P320P7-525AXSP06	314	497.9	377.5	425.7	-	315.4	496	376.8	424.6	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P320P7-532AXSP06	291.7	466.9	352.7	398.7	-	293.2	464.8	352.5	397.4	-	372	21.9	3"	298	14.5	3"	446	30.8	3"
EAW-VD9112P320P7-625AXSP06	341	534.6	407.8	459	-	342.9	532.9	407.2	457.4	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD9112P320P7-632AXSP06	321.1	508.6	386.2	435.7	-	322.9	506.5	386	433.7	-	451	23.1	3"	361	15.2	3"	541	28.9	4"
EAW-VD9112P117F7-425AXSP06	248.1	392.7	297.8	336.5	-	248.5	390.6	296.9	334.5	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD9112P117F7-432AXSP06	229.5	365.6	276.5	312.4	-	230	363.4	275.9	311	-	293	22.9	3"	234	19.4	2"	352	32.2	3"
EAW-VD9112P117F7-525AXSP06	278.1	434.8	332.2	373.1	-	278.8	432.2	330.8	371.2	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD9112P117F7-532AXSP06	261.6	412.4	313.2	353	-	262.1	409.2	312.4	351.2	-	372	23.9	3"	298	15.8	3"	446	33.6	3"
EAW-VD9112P117F7-625AXSP06	299.6	462.4	355.4	398.1	-	300.3	458.8	353.6	395.3	751	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD9112P117F7-632AXSP06	285.1	444.9	340.3	382.3	739.3	285.7	442	339.1	379.6	729.6	451	25.1	3"	361	16.6	3"	541	31.6	4"
EAW-VD9112P24716-425AXSP04	250.8	414.3																	

EAW-VD9112ZA320P7-425AXSP06	330.6	528.4	399.3	451	-	331.5	524.8	398.2	448.5	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD9112ZA320P7-432AXSP06	303.6	487.6	367.3	416.4	-	304.4	485	366.3	414.1	-	406	22.5	3"	325	14.9	3"	487	31.7	3"
EAW-VD9112ZA320P7-525AXSP06	372.2	587.7	447	503.6	-	373.3	583.8	445	500.1	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD9112ZA320P7-532AXSP06	346.2	550.6	416.9	470.7	-	347.2	546.4	415.3	468.5	-	507	24.3	3"	406	16	3"	609	29.4	4"
EAW-VD9112ZA320P7-625AXSP06	404.3	630.6	481.8	541.4	-	405.3	625.1	479.9	538	-	609	21.7	4"	487	17.4	3"	730	30.4	4"
EAW-VD9112ZA320P7-632AXSP06	379.2	597.9	455	513	1001.6	380.1	593.6	453.4	510	987.4	609	21.7	4"	487	17.4	3"	730	30.4	4"
EAW-VD9112ZJ177F7-425AXSP06	292.5	459.8	349.8	393.9	-	292.4	455.4	347.8	390.6	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ177F7-432AXSP06	270.3	428.7	325.3	367.1	-	270.4	425.1	323.2	363.8	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ177F7-525AXSP06	325.7	506.1	387.7	435.1	837.9	325.4	500.7	385.3	430.8	824.6	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ177F7-532AXSP06	304.8	478.5	365.2	410.5	798.7	304.5	474.3	362.7	407.4	786.1	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ177F7-625AXSP08	359.8	548.8	422	470.5	-	357.3	537.6	417.4	464.6	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD9112ZJ177F7-632AXSP08	341.9	522.7	402.8	450.2	-	339.6	515.5	398.9	444.9	-	451	32.4	3"	361	21.4	3"	541	41.7	4"
EAW-VD9112ZJ24716-425AXSP06	318.8	503	381.9	430.7	-	318.7	498.6	380.1	427.5	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ24716-432AXSP06	293.9	467.4	353.8	399.9	-	294	463.1	352	396.8	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ24716-525AXSP06	356.3	554.9	423.8	476.2	-	355.9	549.7	421.8	472.8	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ24716-532AXSP06	333	523.4	398.8	448.8	-	333	518.6	396.5	445.2	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ24716-625AXSP06	383	590.8	454.1	508.4	969.5	382.5	584.8	451.4	504.4	955.1	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD9112ZJ24716-632AXSP06	362.2	564.5	432.6	485.6	936.5	362.2	559.7	429.7	481.3	922.4	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD9112ZJ20P5-425AXSP06	346.2	548.1	416.1	469.1	-	346	543.2	413.3	465.5	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ20P5-432AXSP06	317.8	506.3	382.6	433	-	317.8	501.6	380.5	429.5	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ20P5-525AXSP06	390.3	609.8	465.6	523.7	-	389.6	604.4	463.1	518.9	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ20P5-532AXSP06	362.3	571.5	434.6	489.8	-	362.4	566	432	485.7	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ20P5-625AXSP06	423.6	655	502.7	563.4	-	422.9	647.9	499.5	557.9	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD9112ZJ20P5-632AXSP06	398.5	621.8	475	533.9	-	397.7	615.2	471.5	528.9	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD9112ZJ20P7-425AXSP06	352.8	559.3	424.2	478.4	-	352.8	554.6	421.6	475	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ20P7-432AXSP06	323.7	516.5	390.3	441.5	-	323.8	511.9	387.9	438.1	-	406	24.5	3"	325	16.2	3"	487	34.4	3"
EAW-VD9112ZJ20P7-525AXSP06	397.3	622.3	474.8	533.5	-	397.5	616.2	471.8	529.7	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ20P7-532AXSP06	369.8	582.9	442.9	499.3	-	369.4	577.7	440.5	495.4	-	507	26.3	3"	406	17.3	3"	609	32.2	4"
EAW-VD9112ZJ20P7-625AXSP06	431.6	667	512.4	574.3	-	431.2	661.1	508.6	569	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD9112ZJ20P7-632AXSP06	405.6	633.5	483.6	543.8	-	405.6	627.1	481.1	538.8	-	609	23.6	4"	487	18.7	3"	730	33.2	4"
EAW-VD9114PA177F7-432AXSP04	257.9	422.4	316.9	360.3	724.5	261.5	422.7	318.1	360.5	718.5	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA177F7-432AXSP06	254	404.4	306	345.7	-	254.5	402.5	305	343.9	-	293	23.9	3"	234	20.1	2"	352	33.5	3"
EAW-VD9114PA177F7-525AXSP06	307.1	479.5	366.4	411.6	-	307.8	476.5	365.3	409.5	-	372	24.9	3"	298	16.4	3"	446	34.9	3"
EAW-VD9114PA177F7-532AXSP06	289	455	346.1	389.7	-	289.6	452.4	344.8	387.8	-	372	24.9	3"	298	16.4	3"	446	34.9	3"
EAW-VD9114PA177F7-625AXSP06	329.5	507.8	390.5	437.5	-	330.4	505.3	389.1	435.2	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PA177F7-632AXSP06	315	490	374.9	421.3	-	315.6	486.9	373.6	419.1	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PA24716-425AXSP04	279.9	457.4	342.8	389.9	-	283.8	457.4	344.7	390.5	-	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA24716-432AXSP04	257.2	425.6	317.8	362.1	736.3	261.2	426	319.2	362.4	730.9	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA24716-525AXSP06	333.4	522	397.6	447.3	-	333.9	519.1	396.8	445.3	-	372	24.9	3"	298	16.4	3"	446	34.9	3"
EAW-VD9114PA24716-532AXSP06	312.2	493.2	374.5	422.2	-	313.2	490	373.4	419.9	-	372	24.9	3"	298	16.4	3"	446	34.9	3"
EAW-VD9114PA24716-625AXSP06	359	555	425.7	477.5	-	359.7	551.9	424.6	475.2	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PA24716-632AXSP06	341.7	532.9	407.1	457.4	-	342	529.7	405.9	455.1	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PA320P5-425AXSP04	307.6	502.8	376.3	428.3	-	311.7	502.7	377.7	428.7	-	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA320P5-432AXSP04	281.5	464.8	346.4	394.8	-	285.4	464.4	348.1	395.2	-	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA320P5-525AXSP04	344	558.7	420.4	476.3	-	348.6	558.6	422.3	476.9	-	564	16.8	4"	451	13.6	3"	676	23.6	4"
EAW-VD9114PA320P5-532AXSP04	318.6	523.9	392.6	446	899.9	323.6	523.2	394	446.2	892.1	564	16.8	4"	451	13.6	3"	676	23.6	4"
EAW-VD9114PA320P5-625AXSP06	399.8	621.3	475.5	533.3	-	400.8	617.9	474.3	530.9	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PA320P5-632AXSP06	377.3	590.9	451	506.7	-	377.8	587.3	449.1	504.2	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PA320P7-425AXSP04	312.1	510.3	381.9	434.4	-	316	510.4	383.6	435	-	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA320P7-432AXSP04	285.8	471.6	351.5	400.7	-	289.7	471.5	353	401	-	451	18.6	3"	361	12.3	3"	541	22.6	4"
EAW-VD9114PA320P7-525AXSP04	349.5	567.1	426.5	483.2	-	354.1	567	428.3	483.9	-	564	16.8	4"	451	13.6	3"	676	23.6	4"
EAW-VD9114PA320P7-532AXSP04	323.3	531.4	398.1	452.2	913.5	328.3	531.1	399.6	452.7	906.2	564	16.8	4"	451	13.6	3"	676	23.6	4"
EAW-VD9114PA320P7-625AXSP04	375.3	607	458.7	518.8	1024.1	381.2	606.2	460.6	518.8	1015.3	676	17.6	4"	541	11.6	4"	812	24.8	4"
EAW-VD9114PA320P7-632AXSP06	382.6	599.8	457.5	515	-	383.2	596.3	456.4	512.5	-	451	26.1	3"	361	17.2	3"	541	33	4"
EAW-VD9114PJ177F7-425AXSP04	280.6	452.8	341.1	386.3	-	282.8	451.2	341.4	385.6	-	451	20.2	3"	361	13.3	3"	541	24.7	4"
EAW-VD9114PJ177F7-432AXSP04	258.6	421.9	316.6	359.5	723.4	261.1	420.2	316.9	358.7	715.2	451	20.2	3"	361	13.3	3"	541	24.7	4"
EAW-VD9114PJ177F7-525AXSP04	310.1	497.2	376.6	425.3	836.1	313.4	495	377	424.7	826.5	564	18.3	4"	451	14.7	3"	676	25.7	4"
EAW-VD9114PJ177F7-532AXSP06	310.7	485.7	370.4	416.6	-	310.6	481.8	368.8	413.7	-	372	27.2	3"	298	18	3"	446	38.2	3"
EAW-VD9114PJ177F7-625AXSP06	355.6	544.3	419.8	469.5	-	355.3	540	417.1	465.5	-	451	28.4	3"	361	18.7	3"	541	36.2	4"
EAW-VD9114PJ177F7-632AXSP06	339	524.1	402.4	450.6	-	338.9	519.9	399.8	447.4	-	451	28.4	3"	361	18.7	3"	541	36.2	4"
EAW-VD9114PJ24716-425AXSP04	304.5	491.9	369.6	419.4	-	307	489.9	370.5	418.3	-	451	20.2	3"	361	13.3	3"	541	24.7	4"
EAW-VD9114PJ24716-432AXSP04	280.1	456.4	342.3	388.9	-	283.1	455.2	342.8	388.5	-	451	20.2	3"	361	13.3	3"	541	24.7	4"
EAW-VD9114PJ24716-525AXSP04	337.7	541.5	409.4	463	913.4	341.1	539.6	410.2	462	904.6	564	18.3	4"	451	14.7	3"	676	25.7	4"
EAW-VD9114PJ24716-532AXSP04	315.6	510.9	385.5	436.3	869	319	509.5	386.1	435.8	860.8	564	18.3	4"	451	14.7	3"	676	25.7	4"
EAW-VD9114PJ24716-625AXSP06	387.3	595.6	458.3	512.9	-	387.2	590.3	455.5	509.5	-									

EAW-VD91142A320P7-632AXSP06	452.1	705.6	539.4	605.9	-	452.1	699.5	535.7	601.3	-	609	24.6	4"	487	19.4	3"	730	34.6	4"
EAW-VD91142J177F7-425AXSP06	347.2	542.1	413.6	465.6	-	346.4	536.1	410.4	460.9	-	406	27.8	3"	325	18.4	3"	487	39.1	3"
EAW-VD91142J177F7-432AXSP06	321.5	505.2	384.4	432.8	-	320.2	500	381.2	428.9	-	406	27.8	3"	325	18.4	3"	487	39.1	3"
EAW-VD91142J177F7-525AXSP06	387	596.1	458.3	513.4	-	385.3	589.6	454.1	507.6	-	507	29.6	3"	406	19.5	3"	609	36.8	4"
EAW-VD91142J177F7-532AXSP06	362.8	563.9	431.5	484.8	-	361.6	558.1	427.8	479.6	-	507	29.6	3"	406	19.5	3"	609	36.8	4"
EAW-VD91142J177F7-625AXSP06	415.8	632.6	489	546.1	-	414.1	625.7	485	539.9	1013.8	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J177F7-632AXSP06	394.8	607.5	467.2	523	998.5	393.4	599.9	463.4	517.7	981.3	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J24716-425AXSP04	353.6	571	430.7	487.3	969.9	355.9	568.2	430.5	485.6	958.5	609	18.7	4"	487	15.5	3"	730	26.3	4"
EAW-VD91142J24716-432AXSP06	349.4	551	418.4	471.8	-	348.4	545.8	415.3	467.9	-	406	27.8	3"	325	18.4	3"	487	39.1	3"
EAW-VD91142J24716-525AXSP06	422.9	653.7	501.3	562.1	-	421.6	646.5	497.3	556.4	-	507	29.6	3"	406	19.5	3"	609	36.8	4"
EAW-VD91142J24716-532AXSP06	395.9	617.1	471.4	529.5	-	394.5	610.5	467.9	524.3	-	507	29.6	3"	406	19.5	3"	609	36.8	4"
EAW-VD91142J24716-625AXSP06	455.1	695.3	537.1	600.3	-	453.7	687.4	532.4	593.9	-	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J24716-632AXSP06	431.8	665.8	511.4	573.1	-	430.2	658.2	507.2	567.1	-	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J320P5-425AXSP04	385.4	621.6	468.7	531	-	388	618.5	467.6	528.3	-	609	18.7	4"	487	15.5	3"	730	26.3	4"
EAW-VD91142J320P5-432AXSP04	352	574.7	431.1	489.6	984.3	354.8	570.7	430.6	487	971.7	609	18.7	4"	487	15.5	3"	730	26.3	4"
EAW-VD91142J320P5-525AXSP04	431.4	691	523.4	591.5	1163.9	434.2	686.3	522.7	588.2	1148.8	755	20	4"	604	13.2	4"	906	24.2	(2) 4"
EAW-VD91142J320P5-532AXSP06	430.3	673	514	578.1	-	429.4	666.4	510	572.2	-	507	29.6	3"	406	19.5	3"	609	36.8	4"
EAW-VD91142J320P5-625AXSP06	502.9	771.1	594	664.6	-	501.2	762.7	589.3	657.9	-	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J320P5-632AXSP06	473.1	732.5	561.9	629.4	-	471.2	723.7	556.8	623.3	-	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J320P7-425AXSP04	393.2	634.2	477.6	541.4	-	396.3	631.3	476.8	538.9	-	609	18.7	4"	487	15.5	3"	730	26.3	4"
EAW-VD91142J320P7-432AXSP04	359.1	585	439.6	498.8	1004.9	361.7	582.2	439.3	497.5	992.3	609	18.7	4"	487	15.5	3"	730	26.3	4"
EAW-VD91142J320P7-525AXSP04	439.7	704	533.7	602.4	1188.3	442.9	699.6	532.4	599.3	1171.9	755	20	4"	604	13.2	4"	906	24.2	(2) 4"
EAW-VD91142J320P7-532AXSP06	439.2	686.5	523.9	589.4	-	437.9	680.2	520.1	583.7	-	507	29.6	3"	406	19.5	3"	609	36.8	4"
EAW-VD91142J320P7-625AXSP06	512.5	786.3	605.5	677.5	-	510.3	777.2	600.1	670.2	-	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD91142J320P7-632AXSP06	481.6	746.5	572.2	642	-	479.9	737.8	567.2	635.1	-	609	26.9	4"	487	20.9	3"	730	37.8	4"
EAW-VD9116PA177F7-425AXSP04	304.3	489.4	368.6	417.8	-	307.2	488.8	369.7	417.2	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA177F7-432AXSP04	281.1	457	342.8	389	-	283.7	454.9	343.2	388.5	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA177F7-525AXSP04	335.9	536.1	406.8	458.9	902.8	339.3	534.5	407.1	458.2	893.6	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA177F7-532AXSP04	315.2	508.5	383.8	434.8	863.3	318.5	507.3	384.5	433.7	854.4	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA177F7-625AXSP06	382.1	585.6	451.3	504.8	-	381.9	581.2	449.1	501.4	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD9116PA177F7-632AXSP06	365.2	564.7	433	485.9	-	365.2	561	431.5	482.4	-	451	29.1	3"	361	19.2	3"	541	27.2	4"
EAW-VD9116PA24716-425AXSP04	328.8	530.2	399.1	452.4	-	332	529.2	400.1	452.1	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA24716-432AXSP04	303.9	493.2	370.2	420.4	-	306.5	492.6	370.8	419.8	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA24716-525AXSP04	366.1	583.2	441.7	499.1	-	368.9	581.9	442.5	498.6	-	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA24716-532AXSP04	341.9	550.8	415.6	470.7	937.1	345.4	550.1	416.1	470	928.1	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA24716-625AXSP04	389.8	618.3	470.9	530.3	1032.2	394.1	616.7	471.3	529.6	1022.8	676	19.6	4"	541	12.9	4"	812	27.6	4"
EAW-VD9116PA24716-632AXSP04	369.8	593.1	449.6	507.5	999.8	373.7	591.5	450.1	506.7	989.7	676	19.6	4"	541	12.9	4"	812	27.6	4"
EAW-VD9116PA320P5-425AXSP04	360.3	583.3	437.8	497.1	-	363.5	581.9	438.8	496.6	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA320P5-432AXSP04	330.6	538.4	403.4	458.3	-	333.7	537.3	403.7	458	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA320P5-525AXSP04	404.5	646.7	489.2	552.7	-	407.9	645.4	489.3	552.4	-	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA320P5-532AXSP04	376.5	606.2	456.7	517.5	-	379.7	605.3	457.3	516.6	-	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA320P5-625AXSP04	436.1	691.4	525.3	591.6	-	440.5	689.8	525.9	591	-	676	19.6	4"	541	12.9	4"	812	27.6	4"
EAW-VD9116PA320P5-632AXSP04	410.3	656.9	497.4	562.4	1111.9	414.3	655.3	498.1	561.7	1100.6	676	19.6	4"	541	12.9	4"	812	27.6	4"
EAW-VD9116PA320P7-425AXSP04	365.6	592	444.4	504.3	-	368.7	590.9	445.2	504.1	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA320P7-432AXSP04	335.3	546.3	408.9	465.2	-	338.3	545.5	410	464.8	-	451	20.6	3"	361	13.6	3"	541	25.3	4"
EAW-VD9116PA320P7-525AXSP04	410.1	656.5	496.2	560.9	-	413.7	655.1	497.3	560.5	-	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA320P7-532AXSP04	381.8	616	462.9	524.7	-	385	614.4	463.8	524.1	-	564	18.8	4"	451	14.9	3"	676	26.3	4"
EAW-VD9116PA320P7-625AXSP04	443.6	702.8	533.5	602	-	447.1	700.7	533.9	600.9	-	676	19.6	4"	541	12.9	4"	812	27.6	4"
EAW-VD9116PA320P7-632AXSP04	416.7	667.8	504.4	570.5	1129.2	420.8	665.2	505.3	569.9	1117.8	676	19.6	4"	541	12.9	4"	812	27.6	4"
EAW-VD9116PJ177F7-425AXSP04	328.3	523.5	396.4	447.8	-	330.1	520.8	395.1	446.1	-	451	22.4	3"	361	14.7	3"	541	27.8	4"
EAW-VD9116PJ177F7-432AXSP04	304	487.5	367.9	416.6	-	305.4	485.5	367.1	414.6	-	451	22.4	3"	361	14.7	3"	541	27.8	4"
EAW-VD9116PJ177F7-525AXSP04	364.7	574.8	437.4	492.9	-	366.5	571.4	437	490.5	-	564	20.5	4"	451	16.1	3"	676	28.8	4"
EAW-VD9116PJ177F7-532AXSP04	341.9	544.8	412.5	465.9	918.2	343.9	541.5	412.3	463.7	907	564	20.5	4"	451	16.1	3"	676	28.8	4"
EAW-VD9116PJ177F7-625AXSP04	389	607.8	465.8	522.8	1005.6	391.3	604.7	464.9	520.7	994.3	676	21.4	4"	541	14.1	4"	812	30	4"
EAW-VD9116PJ177F7-632AXSP04	369.3	585	445.3	501.5	975.7	372	581.3	444.7	499.6	964.2	676	21.4	4"	541	14.1	4"	812	30	4"
EAW-VD9116PJ24716-425AXSP04	355.5	568.9	429.8	485.5	-	357.8	565.6	429	484.2	-	451	22.4	3"	361	14.7	3"	541	27.8	4"
EAW-VD9116PJ24716-432AXSP04	328.2	528.7	397.6	450.8	-	330	526.1	397.5	449.1	-	451	22.4	3"	361	14.7	3"	541	27.8	4"
EAW-VD9116PJ24716-525AXSP04	396.2	625.3	475.7	536	-	398.5	623	475	533.8	-	564	20.5	4"	451	16.1	3"	676	28.8	4"
EAW-VD9116PJ24716-532AXSP04	371.3	590.6	447.1	505.7	-	373.5	587.9	446.8	504.1	-	564	20.5	4"	451	16.1	3"	676	28.8	4"
EAW-VD9116PJ24716-625AXSP04	425.1	664.7	508.1	570.9	1103.5	427.3	661.6	507.4	568.8	1090	676	21.4	4"	541	14.1	4"	812	30	4"
EAW-VD9116PJ24716-632AXSP04	402.6	636.5	484.6	545.4	1066	404.7	633.9	483.5	543.8	1054	676	21.4	4"	541	14.1	4"	812	30	4"
EAW-VD9116PJ320P5-425AXSP04	388.7	623.6	470.5	532.6	-	390.7	620.7	469.6	529.9	-	451	22.4	3"	361	14.7	3"	541	27.8	4"
EAW-VD9116PJ320P5-432AXSP04	356.6	575.8	432.6	490.5	-	358.3	573	432.1	488.9	-	451	22.4	3"	361	14.7	3"	541	27.8	4"
EAW-VD9116PJ320P5-525AXSP04	436.9	692.7	525.6	593.2	-	439.4	689.8	524.6	590.5	-	564	20.5	4"	451	16.1	3"	676	28.8	4"
EAW-VD9116																			

EAW-VD9116Z177F7-625AXSP06	481.7	728.2	564.9	629	-	478.3	719.4	558.6	621.8	-	609	30.2	4"	487	23.1	3"	730	42.4	4"
EAW-VD9116Z177F7-632AXSP06	457.9	698.8	539.4	602.7	-	454.8	690	534.1	595.7	-	609	30.2	4"	487	23.1	3"	730	42.4	4"
EAW-VD9116Z124716-425AXSP04	415	660	500.3	564.6	-	416.5	655.5	498.1	561.6	-	609	20.9	4"	487	16.9	3"	730	29.4	4"
EAW-VD9116Z124716-432AXSP04	382	613.4	462.6	523.4	-	383.7	609	461.3	520.4	-	609	20.9	4"	487	16.9	3"	730	29.4	4"
EAW-VD9116Z124716-525AXSP04	460.8	726.6	553.9	622.7	1213.8	462	720.9	551.5	618.6	1196	755	22.2	4"	604	14.6	4"	906	27.3	(2) 4"
EAW-VD9116Z124716-532AXSP04	430.1	685.2	520.1	586.9	1152.5	431.3	680.2	517.5	582.4	1137	755	22.2	4"	604	14.6	4"	906	27.3	(2) 4"
EAW-VD9116Z124716-625AXSP04	496.8	776.8	594.4	668.8	1283.6	498.6	771	592.9	663.7	1263.2	913	19.9	(2) 4"	730	15.7	4"	1096	27.9	(2) 4"
EAW-VD9116Z124716-632AXSP06	499.5	766	589.7	659.6	-	496.8	757.3	584.7	652.7	-	609	30.2	4"	487	23.1	3"	730	42.4	4"
EAW-VD9116Z1320P5-425AXSP04	451	720	543.7	614.6	-	452	713.8	542.2	611.2	-	609	20.9	4"	487	16.9	3"	730	29.4	4"
EAW-VD9116Z1320P5-432AXSP04	413.9	664.1	500.9	567.3	-	415	659.3	499.3	564.1	-	609	20.9	4"	487	16.9	3"	730	29.4	4"
EAW-VD9116Z1320P5-525AXSP04	506.7	799.1	608	684.5	-	507.9	792.2	605	679.5	-	755	22.2	4"	604	14.6	4"	906	27.3	(2) 4"
EAW-VD9116Z1320P5-532AXSP04	469.1	747.7	566.4	638.9	-	470.4	741.9	564.3	634.9	1244	755	22.2	4"	604	14.6	4"	906	27.3	(2) 4"
EAW-VD9116Z1320P5-625AXSP04	550.6	862	658.8	739.9	1427.7	551.7	854	655.7	734.8	1405.5	913	19.9	(2) 4"	730	15.7	4"	1096	27.9	(2) 4"
EAW-VD9116Z1320P5-632AXSP04	515.9	817.4	622.5	700.2	1364.8	517.8	810.1	619.2	695.8	1345	913	19.9	(2) 4"	730	15.7	4"	1096	27.9	(2) 4"
EAW-VD9116Z1320P7-425AXSP04	459.5	733.4	555.2	626.7	-	460.8	728.7	553	623.5	-	609	20.9	4"	487	16.9	3"	730	29.4	4"
EAW-VD9116Z1320P7-432AXSP04	421.4	677.4	510.4	578.3	-	422.8	672.7	508.7	575.2	-	609	20.9	4"	487	16.9	3"	730	29.4	4"
EAW-VD9116Z1320P7-525AXSP04	515.7	814.2	619	698.2	-	517.2	807.7	616.3	693.5	-	755	22.2	4"	604	14.6	4"	906	27.3	(2) 4"
EAW-VD9116Z1320P7-632AXSP04	478.7	762.5	577.1	652.4	-	479.5	755.9	575.4	647.6	-	755	22.2	4"	604	14.6	4"	906	27.3	(2) 4"
EAW-VD9116Z1320P7-625AXSP04	561	877.7	671.4	754.1	1456.4	562.4	870.1	668.6	748.3	1434.4	913	19.9	(2) 4"	730	15.7	4"	1096	27.9	(2) 4"
EAW-VD9116Z1320P7-632AXSP04	525.9	832.8	633.8	714.1	1393.2	528	825.7	631.6	708.9	1371.7	913	19.9	(2) 4"	730	15.7	4"	1096	27.9	(2) 4"
EAW-VD9118PA177F7-425AXSP04	349	556.2	420.9	476.1	-	351	554.5	420.6	474.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD9118PA177F7-432AXSP04	323	518.9	391	442.8	-	325.1	516.5	390.9	441.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD9118PA177F7-525AXSP04	387	609.3	463.6	522.8	-	388.8	606.6	463.1	521	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA177F7-532AXSP04	363.4	577.6	438	494.2	-	365.6	575.3	437.9	492.9	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA177F7-625AXSP04	411.9	642.7	492	552.5	1065.8	414.5	640.6	491.9	551.2	1054.1	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA177F7-632AXSP04	392.6	620.3	472.2	532	1035.9	394.9	617.3	471.6	530.1	1025.3	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA24716-425AXSP04	376.9	602.9	455.2	514.7	-	379.4	601.5	455.3	514.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD9118PA24716-432AXSP04	348.3	561.4	421.9	478.5	-	350.3	559.5	422.1	477.1	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD9118PA24716-525AXSP04	419.1	663.1	503.7	567.8	-	422.2	660.5	503.5	566.2	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA24716-532AXSP04	393	625.9	473.6	535.3	-	395.2	623.9	474.1	534.3	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA24716-625AXSP04	449.7	702.2	536.9	602.7	-	452.3	699.4	536.5	601.7	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA24716-632AXSP04	426.9	674.2	512.5	577.2	-	429	671.3	512.1	576.3	1117.8	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA320P5-425AXSP02	319	594	422.4	494.8	1058.9	337.8	600.1	433.3	502.3	1054.8	902	10.6	(2) 4"	721	9.4	4"	1082	14.9	(2) 4"
EAW-VD9118PA320P5-432AXSP04	379.2	612.6	460.1	521.8	-	381.2	610.2	459.8	520.3	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD9118PA320P5-525AXSP04	463.5	735.6	557.1	629.2	-	466.4	732.8	557.2	627.6	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA320P5-532AXSP04	431.5	689.1	520.9	588.7	-	433.7	686.7	520.3	587.5	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA320P5-625AXSP04	500.3	785.6	598.4	673.6	-	503.5	782.5	598.9	671.7	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA320P5-632AXSP04	471.6	747.1	567.3	640	-	474.2	743.9	567	638.1	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA320P7-425AXSP02	324	603	429.4	502.5	1075.3	343.3	609	440.1	510.5	1071.6	902	10.6	(2) 4"	721	9.4	4"	1082	14.9	(2) 4"
EAW-VD9118PA320P7-432AXSP04	384.7	621.6	467	529.8	-	387	619.3	467	528.6	-	451	22.6	3"	361	14.9	3"	541	28.1	4"
EAW-VD9118PA320P7-525AXSP04	470.1	746.8	566.2	638.5	-	473	744	565.3	636.9	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA320P7-632AXSP04	437.6	700.3	528	598.1	-	439.8	697.2	527.8	596.1	-	564	20.7	4"	451	16.3	3"	676	29.1	4"
EAW-VD9118PA320P7-625AXSP04	508.1	798.5	607.8	684.5	-	511.1	794.9	608	682.1	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA320P7-632AXSP04	479.1	758.3	575.4	649.3	-	481.8	755.2	575.2	647.4	-	676	21.6	4"	541	14.2	4"	812	30.3	4"
EAW-VD9118PA320P7-625AXSP04	375.8	594.8	450.8	509.2	-	376.2	590.6	449.3	506.1	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9118PA177F7-432AXSP04	347.5	554.4	418.9	473.2	-	348.3	551	417.9	470.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9118PA177F7-525AXSP04	417.2	652.2	498.3	559.6	-	418.3	648.3	496.2	556.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9118PA177F7-532AXSP04	392.4	618.7	469.8	529.5	-	393.1	613.9	468.6	526.8	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9118PA177F7-625AXSP04	446.8	690	530.1	593.9	-	447.9	685.5	528.6	590.6	1122.5	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9118PA177F7-632AXSP04	425	663.6	507.3	570.1	1103.3	425.8	659.4	505.6	567	1090.3	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9118PA24716-425AXSP02	325.2	585.2	421.9	490	1030.1	340	589.2	429.7	494.9	1024.3	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9118PA24716-432AXSP04	375.5	600.4	453	512.3	-	376.4	596.3	451.8	510.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9118PA24716-525AXSP04	453.3	710.8	541.3	609.6	-	454.3	706	540.3	606.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9118PA24716-532AXSP04	424.8	670.9	509.3	574.8	-	425.6	667.8	508	571.9	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9118PA24716-625AXSP04	487	754.7	578.3	648.6	-	487.9	749.2	576.6	645.3	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9118PA24716-632AXSP04	462.1	722.3	551.3	620.3	-	463.5	718.2	550	617.4	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9118PA320P5-425AXSP02	358.6	641.2	464	538.8	1131.8	374.1	645.7	472.4	544	1125.1	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9118PA320P5-432AXSP02	324.9	590.8	423.8	493.8	1047.9	340.2	594.8	431.8	499.2	1043.1	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9118PA320P5-525AXSP04	499.4	786.5	598.4	673.9	-	501.3	781.9	597.3	670.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9118PA320P5-532AXSP04	464.7	737.3	559.2	631.1	-	466.4	732.4	557.7	627.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9118PA320P5-625AXSP04	541.1	841.6	644.4	723.7	-	542.3	836.4	641.6	719	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9118PA320P5-632AXSP04	509.7	800	609.1	686.4	-	510.4	795	607.5	681.8	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9118PA320P7-425AXSP02	364.8	651.4	471.9	548.1	1151	380.4	655.2	480.2	553.3	1142.9	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9118PA320P7-432AXSP02	330.7	600.4	430.6	502	1066.3	346.1	604.2	439.9	507.3	1060.1	902	11.6	(2)						

EAW-VD9118ZJ24716-532AXSP04	494.3	778	592.1	666.7	-	494.5	771	589	661.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9118ZJ24716-625AXSP04	571.2	881.7	678.3	759.5	1449.1	571.3	872.9	673.5	752.6	1427.7	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9118ZJ24716-632AXSP04	539.9	843.3	644.9	724.2	1397.7	539.9	835	641.6	718.9	1376.8	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9118ZJ320P5-425AXSP04	515.3	816.8	619.6	698.8	-	516.1	809.6	616.6	693.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9118ZJ320P5-432AXSP04	473.1	754	570.5	644.5	-	473.2	748.4	567.4	639.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9118ZJ320P5-525AXSP04	579.6	906.8	691.7	778.4	-	578.8	897.7	687.1	771.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9118ZJ320P5-532AXSP04	537.6	847.9	645.1	727.4	-	537.8	841.2	641.4	721.4	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9118ZJ320P5-625AXSP04	631.7	977.4	749.8	840.5	-	630.7	968.2	745.1	833.4	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9118ZJ320P5-632AXSP04	593.9	927.4	708.1	796.1	-	592.8	917.8	704.1	789.8	1519	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9118ZJ320P7-425AXSP04	526.1	833.4	631.6	712.6	-	526.3	826.5	629	707.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9118ZJ320P7-432AXSP04	482.4	769.1	581.3	657	-	482.7	763.7	578.4	652.1	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9118ZJ320P7-525AXSP04	590	924.1	705.5	792.9	-	589.6	916.5	701.1	786.1	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9118ZJ320P7-532AXSP04	547.6	864.7	657.3	741.4	-	548.2	858.4	654	735.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9118ZJ320P7-625AXSP04	643.6	996.6	764.1	856.7	-	643	986.5	759.7	850	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9118ZJ320P7-632AXSP04	604.5	944.9	722	812	-	604.6	936.8	717.2	804.7	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120PA177F7-425AXSP04	393.1	623.3	473	533.7	-	394.5	620.2	471.6	531.7	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9120PA177F7-432AXSP04	364.5	582	439.4	496.9	-	365.4	578.1	438.3	495.2	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9120PA177F7-525AXSP04	435.8	683	520.9	585.4	-	437.6	678.8	519.5	583.3	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9120PA177F7-532AXSP04	409.8	648	491.9	554.8	-	411.4	644.2	490.8	552.2	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9120PA177F7-625AXSP04	465.3	719.8	552.2	619.9	-	467.3	716.3	551.2	616.7	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA177F7-632AXSP04	444.2	694.1	530.5	596.5	-	445.9	690.7	528.9	593.4	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA24716-425AXSP02	341.1	612.4	441.9	513.4	1079.3	356.7	616.8	450.7	519.5	1073.6	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9120PA24716-432AXSP04	392.7	628.6	474.4	536.6	-	394.4	625.2	473.4	534.9	-	451	24.6	3"	361	16.2	3"	541	30.9	4"
EAW-VD9120PA24716-525AXSP04	473	742.4	565.3	637	-	474.7	739.3	565	634.1	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9120PA24716-532AXSP04	443.4	701.2	532.1	601	-	444.9	697.7	531.5	597.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9120PA24716-625AXSP04	506.6	786.6	602.8	676.3	-	508.6	782.3	601.3	673.3	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA24716-632AXSP04	481.6	754.7	576	647.4	-	483.8	751.3	574.4	645.2	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA320P5-425AXSP02	377.7	672.1	487.6	566.3	1188.9	393.2	677.3	496.4	571.9	1182	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9120PA320P5-432AXSP02	342.1	620.3	445.8	519.1	1102.4	357.7	624.2	454.5	525.1	1096.9	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9120PA320P5-525AXSP02	420.2	749.3	542.3	628.9	1309.1	439.3	754	552.5	635.6	1302.7	1127	12.3	(2) 4"	902	8.1	(2) 4"	1352	17.3	(2) 4"
EAW-VD9120PA320P5-532AXSP04	486.2	772.3	585.5	661.4	-	487.6	768.2	583.6	658.7	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9120PA320P5-625AXSP04	564	879	672.1	755.2	-	566.5	875.5	671.5	752.9	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA320P5-632AXSP04	532.4	836.5	636.7	716.9	-	534.2	832.8	635.2	714.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA320P7-425AXSP02	383.7	682.5	495.1	575.4	1207.4	399.7	687.4	504.3	581.3	1200.9	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9120PA320P7-432AXSP02	347.9	629	452.5	527.2	1119.2	363.6	634.2	461.8	533.1	1114.4	902	11.6	(2) 4"	721	10	4"	1082	16.3	(2) 4"
EAW-VD9120PA320P7-525AXSP02	426.9	760.3	551	637.7	1329.5	446	765.1	561.1	645.7	1322.9	1127	12.3	(2) 4"	902	8.1	(2) 4"	1352	17.3	(2) 4"
EAW-VD9120PA320P7-532AXSP04	493.2	783.5	593.5	670.7	-	495.5	779.9	592	668.4	-	564	22.7	4"	451	17.6	3"	676	31.9	4"
EAW-VD9120PA320P7-625AXSP04	572.8	893.5	682.7	767.4	-	575	889.3	681.8	764.6	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120PA320P7-632AXSP04	539.9	849	645.9	728.6	-	541.9	845.5	645.5	725.2	-	676	23.6	4"	541	15.5	4"	812	33.1	4"
EAW-VD9120ZA177F7-425AXSP04	460.7	727.4	552.7	623.2	-	461.5	721.4	550.3	618.8	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA177F7-432AXSP04	426	676.8	512.6	579.3	-	426.2	671.9	510.2	574.9	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA177F7-525AXSP04	511.7	796.8	609.6	684.8	-	511.3	789.7	606	679.3	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA177F7-532AXSP04	479.4	753.4	574.1	646.1	-	479.6	747.9	571	641.1	1244.5	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA177F7-625AXSP04	550.3	849.5	654.2	732.2	1395.2	550.6	841.4	649.7	725.9	1373.6	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA177F7-632AXSP04	522	815.3	624.2	700.6	1350.1	522.1	807.6	620.3	694.7	1330.4	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA24716-425AXSP04	501.3	792.9	601.3	679	-	502.1	787.5	599.6	674	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA24716-432AXSP04	462.3	736.2	557.1	629.7	-	462.9	731.7	555.3	625.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA24716-525AXSP04	557.4	871.7	664.9	747.8	-	557.7	864.6	661.7	742.5	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA24716-532AXSP04	521.5	822.1	625.3	704.7	-	521.7	815.9	621.9	699.1	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA24716-625AXSP04	603	931.2	715.4	801.5	-	603.4	923.5	711.6	795.6	1512.3	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA24716-632AXSP04	570	891.2	681.4	765.7	1481.3	570.8	883.6	677.8	759.9	1458.9	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA320P5-425AXSP04	545.5	866.5	656.7	741.4	-	546.2	859.9	653.2	735.5	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA320P5-432AXSP04	500.3	799.3	603.4	683.3	-	501.1	792.9	601.3	678.8	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA320P5-525AXSP04	612.5	961.2	731.6	824.1	-	612.7	952.9	727.8	817.8	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA320P5-532AXSP04	568.8	898.7	683.2	769.8	-	569	891.6	679.2	764.7	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA320P5-625AXSP04	667.6	1035.4	793	889.5	-	667.8	1026.1	789.4	883.6	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA320P5-632AXSP04	627.3	982.5	749.7	842.3	-	628.1	973.5	745.4	836.8	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA320P7-425AXSP02	444.5	799.3	576.3	669.6	1408	446.2	802.8	586.2	675.4	1396.6	1217	12.7	(2) 4"	974	8.4	(2) 4"	1461	17.9	(2) 4"
EAW-VD9120ZA320P7-432AXSP04	509.4	814.3	614.7	695.4	-	510.1	808.3	612.4	691.6	-	609	23.1	4"	487	18.4	3"	730	32.4	4"
EAW-VD9120ZA320P7-525AXSP04	622.5	978	745	838.1	-	623.2	970.1	741.6	832.2	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA320P7-532AXSP04	579.2	916.2	694.8	784.5	-	579.7	907.8	692.2	778.2	-	755	24.4	4"	604	16.1	4"	906	30.4	(2) 4"
EAW-VD9120ZA320P7-625AXSP04	679	1053.8	806.6	905	-	679.5	1044.6	803.2	899.2	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD9120ZA320P7-632AXSP04	638.5	999.3	762	857.7	-	638.7	990.8	758.1	851.3	-	913	22.1	(2) 4"	730	17.1	4"	1096	31	(2) 4"
EAW-VD91S1MA177F7-425AXSP16	-	31.8	-	26.4	57.1	-													

EAW-VD91S3MA24716-525AXSP12	83.2	129.9	99.3	111.5	-	83.2	128.9	98.9	110.7	-	113	26	1-1/2"	90	17.1	1-1/2"	135	36.5	1-1/2"
EAW-VD91S3MA24716-532AXSP12	77.9	122.7	93.2	105.2	-	78	121.8	92.9	104.4	-	113	26	1-1/2"	90	17.1	1-1/2"	135	36.5	1-1/2"
EAW-VD91S3MA320P5-425AXSP08	72.8	122.5	91.1	104.1	211.9	74.4	122.4	91.7	104.2	209.7	146	15.9	2"	117	12.8	1-1/2"	176	22.4	2"
EAW-VD91S3MA320P5-432AXSP12	74.6	119.2	90	101.7	-	74.7	118.3	89.6	101.1	-	90	24.8	1-1/2"	72	16.4	1-1/2"	108	34.8	1-1/2"
EAW-VD91S3MA320P5-525AXSP12	91.4	143.5	109.3	123.1	-	91.4	142.3	108.8	122.2	-	113	26	1-1/2"	90	17.1	1-1/2"	135	36.5	1-1/2"
EAW-VD91S3MA320P5-532AXSP12	85	134.4	102.1	115.2	-	85.2	133.4	101.7	114.4	-	113	26	1-1/2"	90	17.1	1-1/2"	135	36.5	1-1/2"
EAW-VD91S3MA320P7-425AXSP08	74.2	124.6	92.7	106	216.1	75.7	124.6	93.4	106.2	214	146	15.9	2"	117	12.8	1-1/2"	176	22.4	2"
EAW-VD91S3MA320P7-432AXSP12	75.9	121.4	91.6	103.6	-	76.1	120.5	91.3	103.1	-	90	24.8	1-1/2"	72	16.4	1-1/2"	108	34.8	1-1/2"
EAW-VD91S3MA320P7-525AXSP12	93	146	111.3	125.1	-	93.1	144.8	110.8	124.3	-	113	26	1-1/2"	90	17.1	1-1/2"	135	36.5	1-1/2"
EAW-VD91S3MA320P7-532AXSP12	86.5	137	103.9	117.1	-	86.6	135.8	103.4	116.4	-	113	26	1-1/2"	90	17.1	1-1/2"	135	36.5	1-1/2"
EAW-VD91S4MA177F7-425AXSP08	88.1	141.6	107	121	239.8	88.7	140.8	106.8	120.4	236.8	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA177F7-432AXSP08	81.2	131.9	99.3	112.5	224.9	81.8	131.2	99.1	112.2	222.2	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA177F7-525AXSP08	96.8	154.5	117.4	132.4	258.7	97.5	153.4	117.2	131.6	255.2	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA177F7-532AXSP08	90.4	146	110.2	125	246.5	91.3	145.3	110.1	124.4	243.5	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA24716-425AXSP08	96	154.1	116.4	131.6	-	96.7	153.4	116.2	131.2	-	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA24716-432AXSP08	88.4	143.2	107.8	122.4	-	89.1	142.8	107.7	121.9	242.3	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA24716-525AXSP08	105.8	168.6	128.1	144.4	283.6	106.6	167.8	127.8	143.9	279.8	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA24716-532AXSP08	98.7	159.1	120.3	135.9	269.2	99.4	158.2	120.1	135.4	266	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA320P5-425AXSP08	104.8	168.6	127	143.8	-	105.5	167.8	127	143.3	-	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA320P5-432AXSP08	96	155.7	116.9	132.7	-	96.7	154.8	116.8	132.1	-	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA320P5-525AXSP08	116.9	186.1	141	159.3	-	117.5	185.1	140.7	158.4	-	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA320P5-532AXSP08	108	174	131.5	148.8	295.7	108.8	173.3	131.3	148.2	292.1	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA320P7-425AXSP08	106.6	171.6	129.4	146.5	-	107.2	170.8	129.1	145.8	-	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA320P7-432AXSP08	97.9	158.4	119	135	-	98.5	157.7	119	134.6	-	146	19.9	2"	117	15.4	1-1/2"	176	27.9	2"
EAW-VD91S4MA320P7-525AXSP08	118.9	189.4	143.3	161.8	-	119.6	188.3	143.2	161.4	-	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S4MA320P7-532AXSP08	110.2	177.3	133.6	151.3	-	110.8	176.4	133.5	150.8	297.5	180	20.9	2"	144	13.8	2"	216	29.3	2"
EAW-VD91S5MA177F7-425AXSP08	114.3	180.1	137.1	154.3	-	114.3	178.7	136.3	153.3	-	146	23.8	2"	117	18	1-1/2"	176	33.4	2"
EAW-VD91S5MA177F7-432AXSP08	105.7	168	127.3	143.6	-	105.9	166.6	126.5	142.5	-	146	23.8	2"	117	18	1-1/2"	176	33.4	2"
EAW-VD91S5MA177F7-525AXSP08	126.1	196.4	150.2	168.7	-	126.2	194.7	149.4	167.5	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA177F7-532AXSP08	118.2	185.8	141.5	159.3	-	118.3	184.3	140.9	158.2	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA24716-425AXSP08	124.3	196.2	149	168	-	124.3	194.9	148.4	167.1	-	146	23.8	2"	117	18	1-1/2"	176	33.4	2"
EAW-VD91S5MA24716-432AXSP08	114.6	182.6	138.1	155.9	-	114.8	181.3	137.6	155	-	146	23.8	2"	117	18	1-1/2"	176	33.4	2"
EAW-VD91S5MA24716-525AXSP08	137.2	214.7	164	184.2	-	137.4	213	163	182.9	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA24716-532AXSP08	128.5	202.3	153.8	173.4	-	128.6	200.9	153.3	172.3	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA320P5-425AXSP06	127.4	206.4	155.1	175.8	-	128.5	205.5	155.1	175.3	-	192	19.7	2"	153	13	2"	230	27.7	2"
EAW-VD91S5MA320P5-432AXSP08	124.1	198.3	149.7	169.5	-	124.4	196.8	149.1	168.1	-	146	23.8	2"	117	18	1-1/2"	176	33.4	2"
EAW-VD91S5MA320P5-525AXSP08	151	236.8	180.4	202.9	-	150.9	234.8	179.6	201.5	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA320P5-532AXSP08	140.3	221.8	168.3	190	-	140.4	219.8	167.4	188.5	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA320P7-425AXSP06	129.7	210	157.6	179.1	-	130.7	209.1	157.7	178.6	-	192	19.7	2"	153	13	2"	230	27.7	2"
EAW-VD91S5MA320P7-432AXSP08	126.4	201.9	152.4	172.4	-	126.5	200.4	151.9	171.5	-	146	23.8	2"	117	18	1-1/2"	176	33.4	2"
EAW-VD91S5MA320P7-525AXSP08	153.4	241.1	183.6	206.6	-	153.6	239.2	182.8	205.2	-	180	24.8	2"	144	16.4	2"	216	34.9	2"
EAW-VD91S5MA320P7-532AXSP08	142.6	225.7	171.3	193.2	-	142.8	224.1	170.5	192.1	-	180	24.8	2"	144	16.4	2"	216	34.9	2"



Evapco EAW Line Thermal Performance in USGPM - 30% Propylene Glycol as Process Fluid

Range °F	10	10	15	15	9	10	10	15	15	9	First	First	First	Second	Second	Third	Third	Third	
Approach °F	5	10	10	12	18	5	10	10	12	18	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow	
Dry Bulb Temperature °F	77	77	77	77	77	95	95	95	95	95	GPM	PSI	Inlet	GPM	PSI	Inlet	GPM	PSI	
EAW-DD1504X01L17G7-525AXSP08	336.1	570.2	425.2	485.6	987.8	349.6	573.9	431.3	489.1	979.2	654	16.4	4"	523	10.8	4"	784	23	4"
EAW-DD1504X01L17G7-625AXSP12	412.8	650.7	496.1	559.2	-	417	649.1	496.8	557.8	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD1504X01L17G7-632AXSP12	385.8	614.1	465.6	525.9	-	389.9	612.2	466.8	525	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD1508X01L17G7-525AXSP04	666.7	1136.6	844.1	966.2	1967	693.9	1142.3	858	974.9	1952.9	1319	18.2	4"	1055	12	4"	1582	21.1	6"
EAW-DD1508X01L17G7-625AXSP06	820.4	1296	986.1	1111.8	-	828.8	1291.1	987.7	1110.9	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD1508X01L17G7-632AXSP06	766.2	1220.8	926.5	1046.7	-	775.8	1217.1	927.5	1045.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD1512X01L17G7-525AXSP04	1115.3	1783.2	1350.9	1528.3	-	1128.7	1781.5	1353.6	1527	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD1512X01L17G7-625AXSP04	1222.6	1933.1	1472.3	1660.3	-	1235.5	1928.8	1474.9	1656.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD1512X01L17G7-632AXSP04	1141.1	1820.1	1380.3	1559.8	-	1155.7	1817.5	1384.4	1557.7	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3351X030M3-525AXSP12	315.3	500.5	379.9	428.6	-	318.4	498	380.2	427.8	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030M3-625AXSP12	348.6	546.5	417.9	469.9	-	352.1	544	418	468.4	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M3-632AXSP12	326.0	518	394.2	444.7	867.2	329.9	515.1	394	442.7	856.2	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M5-525AXSP12	315.3	500.5	379.9	428.6	-	318.4	498	380.2	427.8	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030M4-625AXSP12	348.6	546.5	417.9	469.9	-	352.1	544	418	468.4	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M4-632AXSP12	326.0	518	394.2	444.7	867.2	329.9	515.1	394	442.7	856.2	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M5-525AXSP12	315.3	500.5	379.9	428.6	-	318.4	498	380.2	427.8	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030M5-625AXSP12	348.6	546.5	417.9	469.9	-	352.1	544	418	468.4	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M5-632AXSP12	326.0	518	394.2	444.7	867.2	329.9	515.1	394	442.7	856.2	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M9-525AXSP12	315.3	500.5	379.9	428.6	-	318.4	498	380.2	427.8	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030M9-625AXSP12	348.6	546.5	417.9	469.9	-	352.1	544	418	468.4	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030M9-632AXSP12	326.0	518	394.2	444.7	867.2	329.9	515.1	394	442.7	856.2	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N3-525AXSP12	304.1	482.6	366.9	413.7	-	306.8	479.8	366.8	412.5	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030N3-625AXSP12	336.1	527.6	403.9	454	875.4	339.4	524.5	402.9	451.9	862.6	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N3-632AXSP12	314.6	498.9	380	428.5	835.4	318	496.3	380.1	426.9	824.1	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N4-525AXSP12	304.1	482.6	366.9	413.7	-	306.8	479.8	366.8	412.5	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030N4-625AXSP12	336.1	527.6	403.9	454	875.4	339.4	524.5	402.9	451.9	862.6	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N4-632AXSP12	314.6	498.9	380	428.5	835.4	318	496.3	380.1	426.9	824.1	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N5-525AXSP12	304.1	482.6	366.9	413.7	-	306.8	479.8	366.8	412.5	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030N5-625AXSP12	336.1	527.6	403.9	454	875.4	339.4	524.5	402.9	451.9	862.6	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N5-632AXSP12	314.6	498.9	380	428.5	835.4	318	496.3	380.1	426.9	824.1	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N9-525AXSP12	304.1	482.6	366.9	413.7	-	306.8	479.8	366.8	412.5	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030N9-625AXSP12	336.1	527.6	403.9	454	875.4	339.4	524.5	402.9	451.9	862.6	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030N9-632AXSP12	314.6	498.9	380	428.5	835.4	318	496.3	380.1	426.9	824.1	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030Q3-525AXSP12	304.1	482.6	366.9	413.7	-	306.8	479.8	366.8	412.5	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030Q3-625AXSP12	336.1	527.6	403.9	454	875.4	339.4	524.5	402.9	451.9	862.6	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030Q3-632AXSP12	314.6	498.9	380	428.5	835.4	318	496.3	380.1	426.9	824.1	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030T3-525AXSP12	315.3	500.5	379.9	428.6	-	318.4	498	380.2	427.8	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030T3-625AXSP12	348.6	546.5	417.9	469.9	-	352.1	544	418	468.4	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030T3-632AXSP12	326.0	518	394.2	444.7	867.2	329.9	515.1	394	442.7	856.2	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X3-625AXSP12	306.9	486.5	370.3	417.5	-	309.9	484.9	370.5	416.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030X3-525AXSP16	316.3	493.6	377.4	424	-	317	489.7	375.8	421.2	-	316	31.1	4"	252	20.6	4"	379	43.6	4"
EAW-DD3351X030X3-625AXSP12	338.0	530.1	405.6	456	880.7	341.8	527.6	405.7	454.5	868.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X3-625AXSP16	351.2	540.4	416.1	466.1	-	351.7	535.7	414.3	462.5	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351X030X3-632AXSP12	317.3	503.5	383.4	432.4	843.3	321.1	501.4	384	430.7	832.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X3-632AXSP16	330.8	513.4	393.6	441.5	-	331.2	509	391.5	438.2	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351X030X4-525AXSP12	306.9	486.5	370.3	417.5	-	309.9	484.9	370.5	416.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030X4-625AXSP12	338.0	530.1	405.6	456	880.7	341.8	527.6	405.7	454.5	868.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X4-632AXSP12	317.3	503.5	383.4	432.4	843.3	321.1	501.4	384	430.7	832.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X5-525AXSP12	306.9	486.5	370.3	417.5	-	309.9	484.9	370.5	416.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030X5-625AXSP12	338.0	530.1	405.6	456	880.7	341.8	527.6	405.7	454.5	868.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X5-632AXSP12	317.3	503.5	383.4	432.4	843.3	321.1	501.4	384	430.7	832.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X9-525AXSP12	306.9	486.5	370.3	417.5	-	309.9	484.9	370.5	416.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030X9-625AXSP12	338.0	530.1	405.6	456	880.7	341.8	527.6	405.7	454.5	868.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030X9-632AXSP12	317.3	503.5	383.4	432.4	843.3	321.1	501.4	384	430.7	832.9	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351X030Y3-525AXSP16	316.3	493.6	377.4	424	-	317	489.7	375.8	421.2	-	316	31.1	4"	252	20.6	4"	379	43.6	4"
EAW-DD3351X030Y3-625AXSP16	351.2	540.4	416.1	466.1	-	351.7	535.7	414.3	462.5	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351X030Y3-632AXSP16	330.8	513.4	393.6	441.5	-	331.2	509	391.5	438.2	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351X030Y3-632AXSP12	329.6	524.8	398.2	449.6	-	333.2	522.4	398.7	448.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030Y3-632AXSP12	329.6	524.8	398.2	449.6	-	333.2	522.4	398.7	448.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030Y3-632AXSP12	329.6	524.8	398.2	449.6	-	333.2	522.4	398.7	448.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030Y3-632AXSP12	329.6	524.8	398.2	449.6	-	333.2	522.4	398.7	448.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351X030Y3-632AXSP12	329.6	524.8	398.2	449.6	-	333.2	522.4	3											

EAW-DD3351XL037X5-525AXSP12	322.0	511.9	388.9	438.8	-	325.4	509.7	389.4	437.6	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL037X5-625AXSP12	356.8	559.1	427.8	481.2	-	359.9	556.6	427.4	479	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL037X5-632AXSP12	333.5	529.8	403.4	454.5	-	337.8	527.9	403.5	453.6	878	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL037X9-525AXSP12	322.0	511.9	388.9	438.8	-	325.4	509.7	389.4	437.6	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL037X9-625AXSP12	356.8	559.1	427.8	481.2	-	359.9	556.6	427.4	479	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL037X9-632AXSP12	333.5	529.8	403.4	454.5	-	337.8	527.9	403.5	453.6	878	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL037Y3-525AXSP12	322.0	511.9	388.9	438.8	-	325.4	509.7	389.4	437.6	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL037Y3-625AXSP16	369.8	570.2	438.4	491.3	-	370.5	565.2	436.5	487.6	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351XL037Y3-632AXSP16	347.4	539.7	413.6	464.2	-	348.1	536	411.6	461	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351XL045M3-525AXSP12	347.5	553.2	419.6	474.1	-	351.2	551.4	420.7	473.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045M3-625AXSP12	385.2	606.8	463.2	520.8	-	389.2	603.8	463.3	519.7	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045M3-632AXSP12	360.6	573.4	435.3	491	-	364.5	571.1	436	490.6	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045M4-525AXSP12	347.5	553.2	419.6	474.1	-	351.2	551.4	420.7	473.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045M4-621AXSP08	337.2	572.3	425.7	487.9	975.5	352.3	575.4	433	491.6	967	789	16.8	4"	631	11.1	4"	947	23.6	4"
EAW-DD3351XL045M4-625AXSP12	385.2	606.8	463.2	520.8	-	389.2	603.8	463.3	519.7	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045M4-632AXSP12	360.6	573.4	435.3	491	-	364.5	571.1	436	490.6	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045M5-525AXSP12	347.5	553.2	419.6	474.1	-	351.2	551.4	420.7	473.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045M5-625AXSP12	385.2	606.8	463.2	520.8	-	389.2	603.8	463.3	519.7	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045M5-632AXSP12	360.6	573.4	435.3	491	-	364.5	571.1	436	490.6	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N3-525AXSP12	336.2	534.9	405.6	458.1	-	339.2	532.4	406.1	457.4	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045N3-625AXSP12	373.8	587	448.4	504.7	-	377	584.2	448	503.1	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N3-625AXSP12	349.0	553.9	421	475.4	-	352.8	551.6	421	473.5	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N4-525AXSP12	336.2	534.9	405.6	458.1	-	339.2	532.4	406.1	457.4	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045N4-625AXSP12	373.8	587	448.4	504.7	-	377	584.2	448	503.1	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N4-632AXSP12	349.0	553.9	421	475.4	-	352.8	551.6	421	473.5	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N5-525AXSP12	336.2	534.9	405.6	458.1	-	339.2	532.4	406.1	457.4	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045N5-625AXSP12	373.8	587	448.4	504.7	-	377	584.2	448	503.1	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N5-632AXSP12	349.0	553.9	421	475.4	-	352.8	551.6	421	473.5	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N9-525AXSP12	336.2	534.9	405.6	458.1	-	339.2	532.4	406.1	457.4	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045N9-625AXSP12	373.8	587	448.4	504.7	-	377	584.2	448	503.1	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045N9-632AXSP12	349.0	553.9	421	475.4	-	352.8	551.6	421	473.5	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045O3-525AXSP12	336.2	534.9	405.6	458.1	-	339.2	532.4	406.1	457.4	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045O3-625AXSP12	373.8	587	448.4	504.7	-	377	584.2	448	503.1	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045O3-632AXSP12	349.0	553.9	421	475.4	-	352.8	551.6	421	473.5	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045T3-525AXSP12	347.5	553.2	419.6	474.1	-	351.2	551.4	420.7	473.3	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045T3-625AXSP12	385.2	606.8	463.2	520.8	-	389.2	603.8	463.3	519.7	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045T3-632AXSP12	360.6	573.4	435.3	491	-	364.5	571.1	436	490.6	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X3-525AXSP12	337.6	537.3	407.4	460.1	-	340.9	535.3	408.2	459.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045X3-625AXSP12	374.4	588.8	449.2	505.6	-	377.8	586.3	449.6	504.2	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X3-625AXSP16	388.3	599.9	461.2	516.4	-	389.1	594.8	458.7	512.6	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351XL045X3-632AXSP12	350.3	556.2	422.7	477.4	-	354.5	554.4	423.1	475.8	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X3-632AXSP16	364.0	566.7	434.3	487.7	-	364.9	562.3	432.4	484.5	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351XL045X4-525AXSP12	337.6	537.3	407.4	460.1	-	340.9	535.3	408.2	459.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045X4-625AXSP12	374.4	588.8	449.2	505.6	-	377.8	586.3	449.6	504.2	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X4-632AXSP12	350.3	556.2	422.7	477.4	-	354.5	554.4	423.1	475.8	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X5-525AXSP12	337.6	537.3	407.4	460.1	-	340.9	535.3	408.2	459.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045X5-625AXSP12	374.4	588.8	449.2	505.6	-	377.8	586.3	449.6	504.2	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X5-632AXSP12	350.3	556.2	422.7	477.4	-	354.5	554.4	423.1	475.8	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X9-525AXSP12	337.6	537.3	407.4	460.1	-	340.9	535.3	408.2	459.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045X9-625AXSP12	374.4	588.8	449.2	505.6	-	377.8	586.3	449.6	504.2	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045X9-632AXSP12	350.3	556.2	422.7	477.4	-	354.5	554.4	423.1	475.8	-	530	23.8	4"	424	15.7	4"	636	33.3	4"
EAW-DD3351XL045Y3-525AXSP12	337.6	537.3	407.4	460.1	-	340.9	535.3	408.2	459.1	-	428	23.6	4"	343	15.6	4"	514	33	4"
EAW-DD3351XL045Y3-625AXSP16	388.3	599.9	461.2	516.4	-	389.1	594.8	458.7	512.6	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3351XL045Y3-632AXSP16	364.0	566.7	434.3	487.7	-	364.9	562.3	432.4	484.5	-	394	31.2	4"	316	20.7	4"	473	43.8	4"
EAW-DD3352XL030M3-525AXSP06	635.9	1008.3	766	865.3	-	642	1004.6	767.6	862.1	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL030M3-625AXSP06	692.0	1087.3	830.9	934.6	-	700.1	1082.3	831.4	931.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M3-632AXSP06	647.8	1030.2	783.4	884	1727.8	655.7	1025.8	784.4	881.6	1705.9	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M4-525AXSP06	635.9	1008.3	766	865.3	-	642	1004.6	767.6	862.1	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL030M4-625AXSP06	692.0	1087.3	830.9	934.6	-	700.1	1082.3	831.4	931.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M4-632AXSP06	647.8	1030.2	783.4	884	1727.8	655.7	1025.8	784.4	881.6	1705.9	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M5-625AXSP06	635.9	1008.3	766	865.3	-	642	1004.6	767.6	862.1	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL030M5-625AXSP06	692.0	1087.3	830.9	934.6	-	700.1	1082.3	831.4	931.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M5-632AXSP06	647.8	1030.2	783.4	884	1727.8	655.7	1025.8	784.4	881.6	1705.9	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M9-525AXSP06	635.9	1008.3	766	865.3	-	642	1004.6	767.6	862.1	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL030M9-625AXSP06	692.0	1087.3	830.9	934.6	-	700.1	1082.3	831.4	931.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030M9-632AXSP06	647.8	1030.2	783.4	884	1														

EAW-DD3352XL030X9-632AXSP06	630.50	1001.3	763.3	859.7	1678	638.2	997.3	763.3	857.5	1657.3	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL030Y3-525AXSP08	642.90	1001.4	766.8	861	-	644.2	993.2	763.2	855	-	654	29.7	4"	523	19.6	4"	784	41.6	4"
EAW-DD3352XL030Y3-625AXSP08	699.40	1076.7	829.9	928.4	-	700.4	1067.3	825.1	921.3	-	789	30.1	4"	631	19.9	4"	947	42.2	4"
EAW-DD3352XL030Y3-632AXSP08	658.50	1022.6	783.6	880.3	-	659.4	1013.9	780.7	873.9	-	789	30.1	4"	631	19.9	4"	947	42.2	4"
EAW-DD3352XL037M3-525AXSP06	664.90	1059	803.1	907.8	-	671.9	1054	803.9	904.9	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037M3-625AXSP06	726.80	1142.7	872	981.4	-	733.6	1137.9	872.8	978.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M3-632AXSP06	679.50	1080.1	821.1	927.3	-	687.2	1076.1	821.5	923.8	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M4-525AXSP06	664.90	1059	803.1	907.8	-	671.9	1054	803.9	904.9	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037M4-625AXSP06	726.80	1142.7	872	981.4	-	733.6	1137.9	872.8	978.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M4-632AXSP06	679.50	1080.1	821.1	927.3	-	687.2	1076.1	821.5	923.8	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M5-525AXSP06	664.90	1059	803.1	907.8	-	671.9	1054	803.9	904.9	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037M5-625AXSP06	726.80	1142.7	872	981.4	-	733.6	1137.9	872.8	978.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M5-632AXSP06	679.50	1080.1	821.1	927.3	-	687.2	1076.1	821.5	923.8	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M9-525AXSP06	664.90	1059	803.1	907.8	-	671.9	1054	803.9	904.9	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037M9-625AXSP06	726.80	1142.7	872	981.4	-	733.6	1137.9	872.8	978.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037M9-632AXSP06	679.50	1080.1	821.1	927.3	-	687.2	1076.1	821.5	923.8	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N3-525AXSP06	656.50	1043	792.7	894.4	-	662.8	1038.8	792.8	890.8	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037N3-625AXSP06	718.70	1129.3	862.1	970.1	-	724.5	1123.3	862	966.4	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N3-632AXSP06	670.00	1065.7	809.3	913.8	-	678.1	1061	810.4	911.2	1766.2	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N4-525AXSP06	656.50	1043	792.7	894.4	-	662.8	1038.8	792.8	890.8	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037N4-625AXSP06	718.70	1129.3	862.1	970.1	-	724.5	1123.3	862	966.4	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N4-632AXSP06	670.00	1065.7	809.3	913.8	-	678.1	1061	810.4	911.2	1766.2	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N5-525AXSP06	656.50	1043	792.7	894.4	-	662.8	1038.8	792.8	890.8	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037N5-625AXSP06	718.70	1129.3	862.1	970.1	-	724.5	1123.3	862	966.4	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N5-632AXSP06	670.00	1065.7	809.3	913.8	-	678.1	1061	810.4	911.2	1766.2	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N9-525AXSP06	656.50	1043	792.7	894.4	-	662.8	1038.8	792.8	890.8	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037N9-625AXSP06	718.70	1129.3	862.1	970.1	-	724.5	1123.3	862	966.4	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037N9-632AXSP06	670.00	1065.7	809.3	913.8	-	678.1	1061	810.4	911.2	1766.2	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037Q3-525AXSP06	656.50	1043	792.7	894.4	-	662.8	1038.8	792.8	890.8	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037Q3-625AXSP06	718.70	1129.3	862.1	970.1	-	724.5	1123.3	862	966.4	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037Q3-632AXSP06	670.00	1065.7	809.3	913.8	-	678.1	1061	810.4	911.2	1766.2	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037T3-525AXSP06	664.90	1059	803.1	907.8	-	671.9	1054	803.9	904.9	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037T3-625AXSP06	726.80	1142.7	872	981.4	-	733.6	1137.9	872.8	978.7	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037T3-632AXSP06	679.50	1080.1	821.1	927.3	-	687.2	1076.1	821.5	923.8	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X3-625AXSP06	649.50	1032.9	784.1	884.6	-	656.3	1028.2	785	883.3	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037X3-525AXSP08	675.20	1052.7	805.9	905.4	-	676.9	1046	802.4	899.5	-	654	29.7	4"	523	19.6	4"	784	41.6	4"
EAW-DD3352XL037X3-625AXSP08	709.20	1113.7	850.5	957	-	715.5	1108.8	851.1	954.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X3-625AXSP08	736.30	1135.9	874.3	978.6	-	737.7	1126.1	869.4	971.2	-	789	30.1	4"	631	19.9	4"	947	42.2	4"
EAW-DD3352XL037X3-632AXSP06	662.60	1053.5	801.6	903.5	1768.4	671.3	1049.8	802.1	901.7	1747.1	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X3-632AXSP08	691.50	1076.3	823.4	925.6	-	692.9	1067.6	820.8	919.3	-	789	30.1	4"	631	19.9	4"	947	42.2	4"
EAW-DD3352XL037X4-525AXSP06	649.50	1032.9	784.1	884.6	-	656.3	1028.2	785	883.3	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037X4-625AXSP06	709.20	1113.7	850.5	957	-	715.5	1108.8	851.1	954.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X4-632AXSP06	662.60	1053.5	801.6	903.5	1768.4	671.3	1049.8	802.1	901.7	1747.1	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X5-525AXSP06	649.50	1032.9	784.1	884.6	-	656.3	1028.2	785	883.3	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037X5-625AXSP06	709.20	1113.7	850.5	957	-	715.5	1108.8	851.1	954.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X5-632AXSP06	662.60	1053.5	801.6	903.5	1768.4	671.3	1049.8	802.1	901.7	1747.1	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X9-525AXSP06	649.50	1032.9	784.1	884.6	-	656.3	1028.2	785	883.3	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL037X9-625AXSP06	709.20	1113.7	850.5	957	-	715.5	1108.8	851.1	954.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037X9-632AXSP06	662.60	1053.5	801.6	903.5	1768.4	671.3	1049.8	802.1	901.7	1747.1	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL037Y3-525AXSP08	675.20	1052.7	805.9	905.4	-	676.9	1046	802.4	899.5	-	654	29.7	4"	523	19.6	4"	784	41.6	4"
EAW-DD3352XL037Y3-625AXSP08	736.30	1135.9	874.3	978.6	-	737.7	1126.1	869.4	971.2	-	789	30.1	4"	631	19.9	4"	947	42.2	4"
EAW-DD3352XL037Y3-632AXSP08	691.50	1076.3	823.4	925.6	-	692.9	1067.6	820.8	919.3	-	789	30.1	4"	631	19.9	4"	947	42.2	4"
EAW-DD3352XL045M3-525AXSP06	701.10	1116.6	846.2	957.5	-	708.4	1112.8	848.3	955.7	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL045M3-625AXSP06	765.70	1207.1	920.8	1037	-	773.6	1202.9	921.1	1033.5	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M3-632AXSP06	716.20	1140	864.8	977.5	-	725.4	1135.5	866.4	975.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M4-525AXSP06	701.10	1116.6	846.2	957.5	-	708.4	1112.8	848.3	955.7	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL045M4-621AXSP06	761.60	1197.7	913.8	1028.6	-	770.1	1193.2	915	1026.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M4-625AXSP06	765.70	1207.1	920.8	1037	-	773.6	1202.9	921.1	1033.5	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M4-632AXSP06	716.20	1140	864.8	977.5	-	725.4	1135.5	866.4	975.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M5-525AXSP06	701.10	1116.6	846.2	957.5	-	708.4	1112.8	848.3	955.7	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL045M5-625AXSP06	765.70	1207.1	920.8	1037	-	773.6	1202.9	921.1	1033.5	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M5-632AXSP06	716.20	1140	864.8	977.5	-	725.4	1135.5	866.4	975.1	-	1060	24	4"	848	15.9	4"	1271	33.7	4"
EAW-DD3352XL045M9-525AXSP06	701.10	1116.6	846.2	957.5	-	708.4	1112.8	848.3	955.7	-	879	23.3	4"	703	15.4	4"	1055	32.6	4"
EAW-DD3352XL045M9-625AXSP06	765.70	1207.1	920.8	1037	-	773.6	1202.9	921.1	1033.5	-	1060	24	4"	848	15.9	4"	1271	33.7	4"

EAW-DD3353XL030M3-625AXSP04	1031.70	1622.3	1239.1	1396.1	-	1044	1617.2	1240	1391.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M3-632AXSP04	965.20	1536.5	1167.6	1317.9	2578.2	977.2	1530.1	1169.4	1314.5	2545.8	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M4-525AXSP04	947.40	1505.9	1143.5	1289.9	-	956.7	1498.2	1144.1	1287.3	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030M4-625AXSP04	1031.70	1622.3	1239.1	1396.1	-	1044	1617.2	1240	1391.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M4-632AXSP04	965.20	1536.5	1167.6	1317.9	2578.2	977.2	1530.1	1169.4	1314.5	2545.8	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M5-525AXSP04	947.40	1505.9	1143.5	1289.9	-	956.7	1498.2	1144.1	1287.3	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030M5-625AXSP04	1031.70	1622.3	1239.1	1396.1	-	1044	1617.2	1240	1391.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M5-632AXSP04	965.20	1536.5	1167.6	1317.9	2578.2	977.2	1530.1	1169.4	1314.5	2545.8	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M9-525AXSP04	947.40	1505.9	1143.5	1289.9	-	956.7	1498.2	1144.1	1287.3	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030M9-625AXSP04	1031.70	1622.3	1239.1	1396.1	-	1044	1617.2	1240	1391.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030M9-632AXSP04	965.20	1536.5	1167.6	1317.9	2578.2	977.2	1530.1	1169.4	1314.5	2545.8	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N3-525AXSP04	914.00	1452.1	1102.4	1244.8	-	923.5	1445.5	1103.8	1241.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030N3-625AXSP04	996.20	1566.4	1197.7	1346.9	2604.3	1006.6	1559.4	1196.8	1341	2569.4	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N3-632AXSP04	929.90	1482	1127.7	1272.2	2483.8	941.9	1474.6	1128.4	1267.7	2450.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N4-525AXSP04	914.00	1452.1	1102.4	1244.8	-	923.5	1445.5	1103.8	1241.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030N4-625AXSP04	996.20	1566.4	1197.7	1346.9	2604.3	1006.6	1559.4	1196.8	1341	2569.4	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N4-632AXSP04	929.90	1482	1127.7	1272.2	2483.8	941.9	1474.6	1128.4	1267.7	2450.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N5-525AXSP04	914.00	1452.1	1102.4	1244.8	-	923.5	1445.5	1103.8	1241.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030N5-625AXSP04	996.20	1566.4	1197.7	1346.9	2604.3	1006.6	1559.4	1196.8	1341	2569.4	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N5-632AXSP04	929.90	1482	1127.7	1272.2	2483.8	941.9	1474.6	1128.4	1267.7	2450.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030N9-525AXSP04	914.00	1452.1	1102.4	1244.8	-	923.5	1445.5	1103.8	1241.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030N9-625AXSP04	996.20	1566.4	1197.7	1346.9	2604.3	1006.6	1559.4	1196.8	1341	2569.4	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Q3-625AXSP04	929.90	1482	1127.7	1272.2	2483.8	941.9	1474.6	1128.4	1267.7	2450.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Q3-525AXSP04	914.00	1452.1	1102.4	1244.8	-	923.5	1445.5	1103.8	1241.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Q3-632AXSP04	996.20	1566.4	1197.7	1346.9	2604.3	1006.6	1559.4	1196.8	1341	2569.4	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Q3-632AXSP04	929.90	1482	1127.7	1272.2	2483.8	941.9	1474.6	1128.4	1267.7	2450.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030T3-525AXSP04	947.40	1505.9	1143.5	1289.9	-	956.7	1498.2	1144.1	1287.3	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030T3-625AXSP04	1031.70	1622.3	1239.1	1396.1	-	1044	1617.2	1240	1391.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030T3-632AXSP04	965.20	1536.5	1167.6	1317.9	2578.2	977.2	1530.1	1169.4	1314.5	2545.8	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030X3-525AXSP04	922.30	1463.8	1112.6	1256.5	-	932.9	1458.7	1113.4	1252.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030X3-625AXSP04	1001.90	1575.7	1204.7	1354.8	2620.1	1013.7	1568.6	1205.3	1350.5	2585.1	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030X3-625AXSP06	1064.20	1627.6	1257.1	1405.9	-	1062.5	1613.1	1247.9	1392.9	-	1060	34	4"	848	22.5	4"	1271	47.7	4"
EAW-DD3353XL030X3-632AXSP04	939.50	1495.6	1137.8	1283.7	2507.3	951.3	1489.8	1138	1278.7	2476.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030X3-632AXSP06	1001.80	1546.6	1187.9	1332.1	-	1001.3	1531.2	1181.6	1320.3	-	1060	34	4"	848	22.5	4"	1271	47.7	4"
EAW-DD3353XL030X4-525AXSP04	922.30	1463.8	1112.6	1256.5	-	932.9	1458.7	1113.4	1252.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030X4-625AXSP04	1001.90	1575.7	1204.7	1354.8	2620.1	1013.7	1568.6	1205.3	1350.5	2585.1	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030X4-632AXSP04	939.50	1495.6	1137.8	1283.7	2507.3	951.3	1489.8	1138	1278.7	2476.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030X5-525AXSP04	922.30	1463.8	1112.6	1256.5	-	932.9	1458.7	1113.4	1252.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030X5-625AXSP04	1001.90	1575.7	1204.7	1354.8	2620.1	1013.7	1568.6	1205.3	1350.5	2585.1	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030X5-625AXSP06	1064.20	1627.6	1257.1	1405.9	-	1062.5	1613.1	1247.9	1392.9	-	1060	34	4"	848	22.5	4"	1271	47.7	4"
EAW-DD3353XL030Y3-525AXSP04	922.30	1463.8	1112.6	1256.5	-	932.9	1458.7	1113.4	1252.2	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-625AXSP06	1064.20	1627.6	1257.1	1405.9	-	1062.5	1613.1	1247.9	1392.9	-	1060	34	4"	848	22.5	4"	1271	47.7	4"
EAW-DD3353XL030Y3-632AXSP06	1001.80	1546.6	1187.9	1332.1	-	1001.3	1531.2	1181.6	1320.3	-	1060	34	4"	848	22.5	4"	1271	47.7	4"
EAW-DD3353XL030Y3-632AXSP04	992.20	1579	1198.7	1353.1	-	1002.8	1571.8	1200.1	1349	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-632AXSP04	1083.50	1704.9	1302.2	1465.8	-	1095.4	1697.9	1301.7	1459.9	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	1012.40	1610.8	1223.7	1382.3	-	1024.1	1605	1226.4	1379.5	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	992.20	1579	1198.7	1353.1	-	1002.8	1571.8	1200.1	1349	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-632AXSP04	1083.50	1704.9	1302.2	1465.8	-	1095.4	1697.9	1301.7	1459.9	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	1012.40	1610.8	1223.7	1382.3	-	1024.1	1605	1226.4	1379.5	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	992.20	1579	1198.7	1353.1	-	1002.8	1571.8	1200.1	1349	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-632AXSP04	1083.50	1704.9	1302.2	1465.8	-	1095.4	1697.9	1301.7	1459.9	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	1012.40	1610.8	1223.7	1382.3	-	1024.1	1605	1226.4	1379.5	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	978.00	1555.3	1181.2	1333.2	-	987.6	1549.1	1181.6	1330.1	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-632AXSP04	1071.50	1684.9	1285.5	1447	-	1080.3	1676.2	1285.5	1441.5	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	998.20	1589.3	1208.2	1362.2	-	1010.6	1582.6	1208.1	1358.6	2635.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	978.00	1555.3	1181.2	1333.2	-	987.6	1549.1	1181.6	1330.1	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-632AXSP04	1071.50	1684.9	1285.5	1447	-	1080.3	1676.2	1285.5	1441.5	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	998.20	1589.3	1208.2	1362.2	-	1010.6	1582.6	1208.1	1358.6	2635.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	978.00	1555.3	1181.2	1333.2	-	987.6	1549.1	1181.6	1330.1	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL030Y3-632AXSP04	1071.50	1684.9	1285.5	1447	-	1080.3	1676.2	1285.5	1441.5	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL030Y3-632AXSP04	998.20	1589.3	1208.2	1362.2	-	1010.6	1582.6	1208.1	1358.6	2635.6	1589	22	6"	1271	17.5	4"	1907	30.8	6"

EAW-DD3353XL045M5-632AXSP04	1068.70	1699.9	1290.8	1457	-	1080.9	1695.9	1293.4	1453.7	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045M9-525AXSP04	1044.30	1664.8	1262.9	1427	-	1055.4	1661.8	1264.1	1424.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045M9-625AXSP04	1141.30	1800.7	1372.8	1546.6	-	1155.1	1794.7	1375.5	1543.6	-	1589	22	6"	1071	17.5	4"	1907	30.8	6"
EAW-DD3353XL045M9-632AXSP04	1068.70	1699.9	1290.8	1457	-	1080.9	1695.9	1293.4	1453.7	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N3-525AXSP04	1010.20	1609.7	1220.9	1378.7	-	1021	1604.4	1222.2	1376.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045N3-625AXSP04	1107.40	1744.3	1329.3	1499.1	-	1117.6	1736.4	1330.4	1492.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N3-632AXSP04	1032.70	1644.7	1248.7	1408.6	-	1044.5	1636.1	1249.2	1405.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N4-625AXSP04	1107.40	1744.3	1329.3	1499.1	-	1117.6	1736.4	1330.4	1492.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N4-632AXSP04	1032.70	1644.7	1248.7	1408.6	-	1044.5	1636.1	1249.2	1405.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N5-525AXSP04	1010.20	1609.7	1220.9	1378.7	-	1021	1604.4	1222.2	1376.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045N5-625AXSP04	1107.40	1744.3	1329.3	1499.1	-	1117.6	1736.4	1330.4	1492.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N5-632AXSP04	1032.70	1644.7	1248.7	1408.6	-	1044.5	1636.1	1249.2	1405.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N9-525AXSP04	1010.20	1609.7	1220.9	1378.7	-	1021	1604.4	1222.2	1376.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045N9-625AXSP04	1107.40	1744.3	1329.3	1499.1	-	1117.6	1736.4	1330.4	1492.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045N9-632AXSP04	1032.70	1644.7	1248.7	1408.6	-	1044.5	1636.1	1249.2	1405.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045Q3-525AXSP04	1010.20	1609.7	1220.9	1378.7	-	1021	1604.4	1222.2	1376.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045Q3-625AXSP04	1107.40	1744.3	1329.3	1499.1	-	1117.6	1736.4	1330.4	1492.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045Q3-632AXSP04	1032.70	1644.7	1248.7	1408.6	-	1044.5	1636.1	1249.2	1405.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045T3-525AXSP04	1044.30	1664.8	1262.9	1427	-	1055.4	1661.8	1264.1	1424.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045T3-625AXSP04	1141.30	1800.7	1372.8	1546.6	-	1155.1	1794.7	1375.5	1543.6	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045T3-632AXSP04	1068.70	1699.9	1290.8	1457	-	1080.9	1695.9	1293.4	1453.7	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X3-525AXSP04	1014.50	1616.9	1226.2	1384.8	-	1026.2	1610.5	1228.5	1381.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045X3-625AXSP04	1109.10	1747.4	1333.5	1501.7	-	1121.7	1740.5	1335.2	1497.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X3-632AXSP04	1036.70	1651.5	1253.7	1414.4	-	1049.5	1644.2	1255.2	1412.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X4-525AXSP04	1014.50	1616.9	1226.2	1384.8	-	1026.2	1610.5	1228.5	1381.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045X4-625AXSP04	1109.10	1747.4	1333.5	1501.7	-	1121.7	1740.5	1335.2	1497.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X4-632AXSP04	1036.70	1651.5	1253.7	1414.4	-	1049.5	1644.2	1255.2	1412.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X5-525AXSP04	1014.50	1616.9	1226.2	1384.8	-	1026.2	1610.5	1228.5	1381.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045X5-625AXSP04	1109.10	1747.4	1333.5	1501.7	-	1121.7	1740.5	1335.2	1497.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X5-632AXSP04	1036.70	1651.5	1253.7	1414.4	-	1049.5	1644.2	1255.2	1412.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X9-525AXSP04	1014.50	1616.9	1226.2	1384.8	-	1026.2	1610.5	1228.5	1381.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045X9-625AXSP04	1109.10	1747.4	1333.5	1501.7	-	1121.7	1740.5	1335.2	1497.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045X9-632AXSP04	1036.70	1651.5	1253.7	1414.4	-	1049.5	1644.2	1255.2	1412.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045Y3-525AXSP04	1014.50	1616.9	1226.2	1384.8	-	1026.2	1610.5	1228.5	1381.5	-	1319	24.8	4"	1055	16.4	4"	1582	30.4	6"
EAW-DD3353XL045Y3-625AXSP04	1109.10	1747.4	1333.5	1501.7	-	1121.7	1740.5	1335.2	1497.8	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-DD3353XL045Y3-632AXSP04	1036.70	1651.5	1253.7	1414.4	-	1049.5	1644.2	1255.2	1412.4	-	1589	22	6"	1271	17.5	4"	1907	30.8	6"
EAW-FD1551PB370C2-425AXSP16	33.10	58.1	42.7	49.2	102.2	35.1	59.1	43.9	50.2	102.5	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C2-432AXSP16	30.60	54.5	39.8	46.1	96.7	32.5	55.3	40.9	46.9	96.6	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C2-525AXSP16	35.70	62.7	46.1	53.2	109.1	38	63.8	47.4	54.3	109.4	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C2-532AXSP16	33.60	60	43.7	50.6	105.2	35.9	61	45	51.7	105.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C2-625AXSP16	37.00	65.2	47.8	55.1	112.2	39.7	66.4	49.4	56.4	112.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C2-632AXSP16	35.40	63.5	46.2	53.5	110.4	38.1	64.5	47.7	54.7	110.5	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C4-425AXSP16	33.10	58.1	42.7	49.2	102.2	35.1	59.1	43.9	50.2	102.5	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C4-432AXSP16	30.60	54.5	39.8	46.1	96.7	32.5	55.3	40.9	46.9	96.6	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C4-525AXSP16	35.70	62.7	46.1	53.2	109.1	38	63.8	47.4	54.3	109.4	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C4-532AXSP16	33.60	60	43.7	50.6	105.2	35.9	61	45	51.7	105.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C4-625AXSP16	37.00	65.2	47.8	55.1	112.2	39.7	66.4	49.4	56.4	112.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C4-632AXSP16	35.40	63.5	46.2	53.5	110.4	38.1	64.5	47.7	54.7	110.5	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C5-425AXSP16	33.10	58.1	42.7	49.2	102.2	35.1	59.1	43.9	50.2	102.5	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C5-432AXSP16	30.60	54.5	39.8	46.1	96.7	32.5	55.3	40.9	46.9	96.6	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C5-525AXSP16	35.70	62.7	46.1	53.2	109.1	38	63.8	47.4	54.3	109.4	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C5-532AXSP16	33.60	60	43.7	50.6	105.2	35.9	61	45	51.7	105.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C5-625AXSP16	37.00	65.2	47.8	55.1	112.2	39.7	66.4	49.4	56.4	112.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C5-632AXSP16	35.40	63.5	46.2	53.5	110.4	38.1	64.5	47.7	54.7	110.5	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C8-425AXSP16	33.10	58.1	42.7	49.2	102.2	35.1	59.1	43.9	50.2	102.5	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C8-432AXSP16	30.60	54.5	39.8	46.1	96.7	32.5	55.3	40.9	46.9	96.6	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370C8-525AXSP16	35.70	62.7	46.1	53.2	109.1	38	63.8	47.4	54.3	109.4	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C8-532AXSP16	33.60	60	43.7	50.6	105.2	35.9	61	45	51.7	105.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370C8-625AXSP16	37.00	65.2	47.8	55.1	112.2	39.7	66.4	49.4	56.4	112.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370C8-632AXSP16	35.40	63.5	46.2	53.5	110.4	38.1	64.5	47.7	54.7	110.5	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD1551PB370K2-425AXSP16	32.40	56.8	41.7	48.1	100	34.2	57.6	42.8	49	99.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370K2-432AXSP16	29.70	53.1	38.7	44.9	94	31.6	53.9	39.8	45.7	94	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD1551PB370K2-442AXSP16	35.20	62	45.4	52.5	107.7	37.4	62.8	46.7	53.5	107.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD1551PB370K2-532AXSP16	32.90	58.8	42.8	49.6	103	35													

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1PB400C9-625AXSP16	37.00	65.2	47.8	55.1	112.2	39.7	66.4	49.4	56.4	112.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400C9-632AXSP16	35.40	63.5	46.2	53.5	110.4	38.1	64.5	47.7	54.7	110.5	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400K3-425AXSP16	32.40	56.8	41.7	48.1	100	34.2	57.6	42.8	49	99.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB400K3-432AXSP16	29.70	53.1	38.7	44.9	94	31.6	53.9	39.8	45.7	94	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB400K3-525AXSP16	35.20	62	45.4	52.5	107.7	37.4	62.8	46.7	53.5	107.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB400K3-532AXSP16	32.90	58.8	42.8	49.6	103	35	59.7	44	50.5	103	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB400K3-625AXSP16	36.90	65.1	47.7	55	111.9	39.5	66	49.1	56.1	111.7	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400K3-632AXSP16	34.90	62.6	45.6	52.8	109.1	37.6	63.7	47	53.9	108.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400K9-425AXSP16	32.40	56.8	41.7	48.1	100	34.2	57.6	42.8	49	99.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB400K9-432AXSP16	29.70	53.1	38.7	44.9	94	31.6	53.9	39.8	45.7	94	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB400K9-525AXSP16	35.20	62	45.4	52.5	107.7	37.4	62.8	46.7	53.5	107.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB400K9-532AXSP16	32.90	58.8	42.8	49.6	103	35	59.7	44	50.5	103	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB400K9-625AXSP16	36.90	65.1	47.7	55	111.9	39.5	66	49.1	56.1	111.7	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400K9-632AXSP16	34.90	62.6	45.6	52.8	109.1	37.6	63.7	47	53.9	108.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400R3-425AXSP16	32.70	57.4	42.2	48.7	101.1	34.6	58.3	43.3	49.5	101	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB400R3-432AXSP16	30.10	53.7	39.2	45.4	95.1	31.9	54.5	40.2	46.2	95.1	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB400R3-525AXSP16	35.60	62.5	45.8	53	108.7	37.8	63.4	47.2	53.9	108.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB400R3-532AXSP16	33.20	59.4	43.3	50.1	104.1	35.4	60.3	44.5	51.1	104.1	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB400R3-625AXSP16	37.20	65.7	48.1	55.5	112.9	39.8	66.7	49.6	56.6	112.8	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB400R3-632AXSP16	35.30	63.3	46	53.4	110	37.9	64.2	47.5	54.4	109.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550B3-425AXSP16	34.30	60	44.2	50.8	105.8	36.3	61	45.4	51.8	106	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550B3-432AXSP16	31.80	56.4	41.3	47.7	100.1	33.7	57.4	42.5	48.6	100.3	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550B3-525AXSP16	-	-	-	-	-	-	-	-	-	-	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550B3-532AXSP16	-	-	-	-	-	37	62.9	46.5	53.4	108.8	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550B3-632AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550B3-632AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C2-425AXSP16	37.00	64.3	47.4	54.5	-	39	65.4	48.6	55.5	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C2-432AXSP16	34.00	60	44	50.7	106.6	35.9	61	45.2	51.7	106.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C2-525AXSP16	40.00	69.8	51.5	59.2	121.7	42.4	70.9	52.9	60.4	122	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C2-532AXSP16	37.50	66.4	48.5	56.2	116.7	39.8	67.4	50	57.3	116.9	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C2-632AXSP16	-	-	-	-	-	42.5	71.8	53.2	60.9	123.2	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C3-425AXSP16	37.00	64.3	47.4	54.5	-	39	65.4	48.6	55.5	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C3-432AXSP16	34.00	60	44	50.7	106.6	35.9	61	45.2	51.7	106.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C3-525AXSP16	40.00	69.8	51.5	59.2	121.7	42.4	70.9	52.9	60.4	122	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C3-532AXSP16	37.50	66.4	48.5	56.2	116.7	39.8	67.4	50	57.3	116.9	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C3-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C3-632AXSP16	-	-	-	-	-	42.5	71.8	53.2	60.9	123.2	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C4-425AXSP16	37.00	64.3	47.4	54.5	-	39	65.4	48.6	55.5	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C4-432AXSP16	34.00	60	44	50.7	106.6	35.9	61	45.2	51.7	106.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C4-525AXSP16	40.00	69.8	51.5	59.2	121.7	42.4	70.9	52.9	60.4	122	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C4-532AXSP16	37.50	66.4	48.5	56.2	116.7	39.8	67.4	50	57.3	116.9	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C4-632AXSP16	-	-	-	-	-	42.5	71.8	53.2	60.9	123.2	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C5-425AXSP16	37.00	64.3	47.4	54.5	-	39	65.4	48.6	55.5	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C5-432AXSP16	34.00	60	44	50.7	106.6	35.9	61	45.2	51.7	106.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C5-525AXSP16	40.00	69.8	51.5	59.2	121.7	42.4	70.9	52.9	60.4	122	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C5-532AXSP16	37.50	66.4	48.5	56.2	116.7	39.8	67.4	50	57.3	116.9	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C5-632AXSP16	-	-	-	-	-	42.5	71.8	53.2	60.9	123.2	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C8-425AXSP16	37.00	64.3	47.4	54.5	-	39	65.4	48.6	55.5	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C8-432AXSP16	34.00	60	44	50.7	106.6	35.9	61	45.2	51.7	106.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C8-525AXSP16	40.00	69.8	51.5	59.2	121.7	42.4	70.9	52.9	60.4	122	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C8-532AXSP16	37.50	66.4	48.5	56.2	116.7	39.8	67.4	50	57.3	116.9	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C8-632AXSP16	-	-	-	-	-	42.5	71.8	53.2	60.9	123.2	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C9-425AXSP16	37.00	64.3	47.4	54.5	-	39	65.4	48.6	55.5	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C9-432AXSP16	34.00	60	44	50.7	106.6	35.9	61	45.2	51.7	106.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550C9-525AXSP16	40.00	69.8	51.5	59.2	121.7	42.4	70.9	52.9	60.4	122	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C9-532AXSP16	37.50	66.4	48.5	56.2	116.7	39.8	67.4	50	57.3	116.9	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550C9-625AXSP16	-	-	-	-	-	-	-	-	-	-	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550C9-632AXSP16	-	-	-	-	-	42.5	71.8	53.2	60.9	123.2	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550K2-425AXSP16	35.50	61.8	45.6	52.4	109.1	37.4	62.9	46.7	53.3	109.2	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550K2-432AXSP16	32.60	57.7	42.2	48.8	102.3	34.4	58.6	43.4	49.7	102.4	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550K2-525AXSP16	38.60	67.4	49.7	57.2	117.5	40.9	68.5	51	58.3	117.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550K2-532AXSP16	36.00	64	46.7	54.1	112.4	38.3	64.9	48.1	55.2	112.5	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB550K2-625AXSP16	40.50	71	52.2	60.1	122.2	43.2	72.1	53.7	61.3	122.3	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550K2-632AXSP16	38.30	68.3	49.7	57.7	118.8	41	69.3	51.3	58.8	118.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB550K3-425AXSP16	35.50	61.8	45.6	52.4	109.1	37.4	62.9	46.7	53.3	109.2	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550K3-432AXSP16	32.60	57.7	42.2	48.8	102.3	34.4	58.6	43.4	49.7	102.4	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB550K3-525AXSP16	38.60	6																	

EAW-FD15S1PB750K2-432AXSP16	34.40	60.6	44.5	51.3	107.8	36.3	61.7	45.7	52.2	108	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K2-525AXSP16	40.60	70.6	52.1	60	123.5	43	71.8	53.7	61.2	123.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K2-532AXSP16	37.90	67.1	49.1	56.9	118	40.3	68.2	50.6	57.9	118.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K2-625AXSP16	42.50	74.2	54.6	63	128.2	45.2	75.4	56.3	64.2	128.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K2-632AXSP16	40.30	71.5	52.3	60.4	124.6	43	72.7	53.9	61.7	124.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K3-425AXSP16	37.40	65	47.9	55.1	-	39.5	66.2	49.1	56.1	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K3-432AXSP16	34.40	60.6	44.5	51.3	107.8	36.3	61.7	45.7	52.2	108	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K3-525AXSP16	40.60	70.6	52.1	60	123.5	43	71.8	53.7	61.2	123.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K3-532AXSP16	37.90	67.1	49.1	56.9	118	40.3	68.2	50.6	57.9	118.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K3-625AXSP16	42.50	74.2	54.6	63	128.2	45.2	75.4	56.3	64.2	128.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K3-632AXSP16	40.30	71.5	52.3	60.4	124.6	43	72.7	53.9	61.7	124.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K4-425AXSP16	37.40	65	47.9	55.1	-	39.5	66.2	49.1	56.1	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K4-432AXSP16	34.40	60.6	44.5	51.3	107.8	36.3	61.7	45.7	52.2	108	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K4-525AXSP16	40.60	70.6	52.1	60	123.5	43	71.8	53.7	61.2	123.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K4-532AXSP16	37.90	67.1	49.1	56.9	118	40.3	68.2	50.6	57.9	118.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K4-625AXSP16	42.50	74.2	54.6	63	128.2	45.2	75.4	56.3	64.2	128.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K4-632AXSP16	40.30	71.5	52.3	60.4	124.6	43	72.7	53.9	61.7	124.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K5-425AXSP16	37.40	65	47.9	55.1	-	39.5	66.2	49.1	56.1	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K5-432AXSP16	34.40	60.6	44.5	51.3	107.8	36.3	61.7	45.7	52.2	108	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K5-525AXSP16	40.60	70.6	52.1	60	123.5	43	71.8	53.7	61.2	123.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K5-532AXSP16	37.90	67.1	49.1	56.9	118	40.3	68.2	50.6	57.9	118.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K5-625AXSP16	42.50	74.2	54.6	63	128.2	45.2	75.4	56.3	64.2	128.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K5-632AXSP16	40.30	71.5	52.3	60.4	124.6	43	72.7	53.9	61.7	124.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K8-425AXSP16	37.40	65	47.9	55.1	-	39.5	66.2	49.1	56.1	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K8-432AXSP16	34.40	60.6	44.5	51.3	107.8	36.3	61.7	45.7	52.2	108	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K8-525AXSP16	40.60	70.6	52.1	60	123.5	43	71.8	53.7	61.2	123.6	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K8-532AXSP16	37.90	67.1	49.1	56.9	118	40.3	68.2	50.6	57.9	118.3	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750K8-625AXSP16	42.50	74.2	54.6	63	128.2	45.2	75.4	56.3	64.2	128.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K8-632AXSP16	40.30	71.5	52.3	60.4	124.6	43	72.7	53.9	61.7	124.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K9-425AXSP16	37.40	65	47.9	55.1	-	39.5	66.2	49.1	56.1	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750K9-525AXSP16	42.50	74.2	54.6	63	128.2	45.2	75.4	56.3	64.2	128.4	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K9-625AXSP16	40.30	71.5	52.3	60.4	124.6	43	72.7	53.9	61.7	124.9	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750K9-632AXSP16	37.40	65	47.9	55.1	-	39.5	66.2	49.1	56.1	-	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750R3-425AXSP16	36.60	63.7	47	54	112.5	38.6	64.8	48.2	55	112.8	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750R3-432AXSP16	33.70	59.5	43.6	50.3	105.7	35.6	60.5	44.8	51.3	106	68	21.5	1-1/2"	54	14.1	1-1/2"	81	25.4	2"
EAW-FD15S1PB750R3-525AXSP16	39.70	69.2	51	58.8	120.9	42.1	70.4	52.5	60	121.2	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750R3-532AXSP16	37.10	65.8	48.1	55.7	115.6	39.5	66.9	49.5	56.8	116	84	19.1	2"	68	16	1-1/2"	101	26.9	2"
EAW-FD15S1PB750R3-625AXSP16	41.60	72.8	53.5	61.7	125.5	44.3	73.9	55.1	63	125.7	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1PB750R3-632AXSP16	39.40	70.1	51.1	59.2	122	42.1	71.2	52.8	60.5	122.3	101	20.4	2"	81	13.4	2"	122	23.9	3"
EAW-FD15S1ZB370C2-425AXSP16	35.00	61.6	45.3	52.2	108.4	37.1	62.6	46.5	53.2	108.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C2-432AXSP16	32.20	57.6	42	48.7	102.1	34.2	58.4	43.1	49.5	102	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C2-525AXSP16	37.70	66.5	48.7	56.3	115.7	40.1	67.5	50.1	57.5	115.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C2-532AXSP16	35.30	63.3	46	53.4	111	37.6	64.1	47.3	54.3	111	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C2-625AXSP16	40.20	71	52.1	60.1	122.3	43.1	72.3	53.7	61.4	122.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C2-632AXSP16	38.30	68.9	50.1	58	119.7	41.2	70	51.7	59.2	119.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C4-425AXSP16	35.00	61.6	45.3	52.2	108.4	37.1	62.6	46.5	53.2	108.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C4-432AXSP16	32.20	57.6	42	48.7	102.1	34.2	58.4	43.1	49.5	102	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C4-525AXSP16	37.70	66.5	48.7	56.3	115.7	40.1	67.5	50.1	57.5	115.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C4-532AXSP16	35.30	63.3	46	53.4	111	37.6	64.1	47.3	54.3	111	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C4-625AXSP16	40.20	71	52.1	60.1	122.3	43.1	72.3	53.7	61.4	122.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C4-632AXSP16	38.30	68.9	50.1	58	119.7	41.2	70	51.7	59.2	119.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C5-425AXSP16	35.00	61.6	45.3	52.2	108.4	37.1	62.6	46.5	53.2	108.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C5-432AXSP16	32.20	57.6	42	48.7	102.1	34.2	58.4	43.1	49.5	102	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C5-525AXSP16	37.70	66.5	48.7	56.3	115.7	40.1	67.5	50.1	57.5	115.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C5-532AXSP16	35.30	63.3	46	53.4	111	37.6	64.1	47.3	54.3	111	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C5-625AXSP16	40.20	71	52.1	60.1	122.3	43.1	72.3	53.7	61.4	122.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C5-632AXSP16	38.30	68.9	50.1	58	119.7	41.2	70	51.7	59.2	119.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C8-425AXSP16	35.00	61.6	45.3	52.2	108.4	37.1	62.6	46.5	53.2	108.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C8-432AXSP16	32.20	57.6	42	48.7	102.1	34.2	58.4	43.1	49.5	102	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370C8-525AXSP16	37.70	66.5	48.7	56.3	115.7	40.1	67.5	50.1	57.5	115.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C8-532AXSP16	35.30	63.3	46	53.4	111	37.6	64.1	47.3	54.3	111	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB370C8-625AXSP16	40.20	71	52.1	60.1	122.3	43.1	72.3	53.7	61.4	122.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370C8-632AXSP16	38.30	68.9	50.1	58	119.7	41.2	70	51.7	59.2	119.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB370K2-425AXSP16	34.00	59.9	43.9	50.7	105.3	35.9	60.7	45	51.6	105.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB370K2-432AXSP16	31.20	55.8	40.6	47.2	98.9	33.1	56.6	41.7	4										

EAW-FD15S1ZB400C9-425AXSP16	35.00	61.6	45.3	52.2	108.4	37.1	62.6	46.5	53.2	108.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400C9-432AXSP16	32.20	57.6	42	48.7	102.1	34.2	58.4	43.1	49.5	102	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400C9-525AXSP16	37.70	66.5	48.7	56.3	115.7	40.1	67.5	50.1	57.5	115.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400C9-532AXSP16	35.30	63.3	46	53.4	111	37.6	64.1	47.3	54.3	111	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400C9-625AXSP16	40.20	71	52.1	60.1	122.3	43.1	72.3	53.7	61.4	122.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400C9-632AXSP16	38.30	68.9	50.1	58	119.7	41.2	70	51.7	59.2	119.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400K3-425AXSP16	34.00	59.9	43.9	50.7	105.3	35.9	60.7	45	51.6	105.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400K3-432AXSP16	31.20	55.8	40.6	47.2	98.9	33.1	56.6	41.7	48	98.8	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400K3-525AXSP16	36.80	65	47.6	55	113	39.1	65.9	48.9	56	112.9	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400K3-532AXSP16	34.20	61.5	44.7	51.8	108	36.5	62.4	46	52.7	107.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400K3-625AXSP16	39.60	70	51.2	59.2	120.5	42.3	71	52.8	60.2	120.2	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400K3-632AXSP16	-	67.2	48.9	56.7	117.1	40.2	68.2	50.4	57.8	116.8	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400K9-425AXSP16	34.00	59.9	43.9	50.7	105.3	35.9	60.7	45	51.6	105.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400K9-432AXSP16	31.20	55.8	40.6	47.2	98.9	33.1	56.6	41.7	48	98.8	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400K9-525AXSP16	36.80	65	47.6	55	113	39.1	65.9	48.9	56	112.9	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400K9-532AXSP16	34.20	61.5	44.7	51.8	108	36.5	62.4	46	52.7	107.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400K9-625AXSP16	39.60	70	51.2	59.2	120.5	42.3	71	52.8	60.2	120.2	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400K9-632AXSP16	-	67.2	48.9	56.7	117.1	40.2	68.2	50.4	57.8	116.8	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400R3-425AXSP16	34.40	60.6	44.5	51.3	106.6	36.4	61.4	45.6	52.2	106.6	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400R3-432AXSP16	31.60	56.5	41.1	47.8	100.2	33.5	57.3	42.3	48.6	100.1	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB400R3-525AXSP16	37.20	65.7	48.1	55.7	114.3	39.6	66.6	49.4	56.6	114.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400R3-532AXSP16	34.70	62.3	45.2	52.4	109.3	37	63.2	46.5	53.4	109	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB400R3-625AXSP16	40.00	70.7	51.8	59.8	121.7	42.9	71.8	53.3	60.9	121.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB400R3-632AXSP16	37.90	68	49.5	57.3	118.4	40.7	69.1	51	58.5	118.1	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550B3-425AXSP16	36.50	64.1	47.1	54.3	113	38.6	65.1	48.4	55.3	113.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550B3-432AXSP16	33.70	60	43.8	50.7	106.4	35.7	61	45	51.6	106.6	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550B3-525AXSP16	39.10	68.7	50.5	58.3	119.9	41.6	69.9	51.9	59.5	120	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550B3-532AXSP16	36.70	65.5	47.8	55.4	115.1	39.1	66.6	49.2	56.5	115.5	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550B3-625AXSP16	-	-	-	-	-	-	-	-	-	-	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550B3-632AXSP16	-	-	-	-	-	42.7	72.4	53.5	61.3	124	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C2-432AXSP16	39.20	68.3	50.3	57.8	120.8	41.3	69.3	51.6	58.9	120.9	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C2-425AXSP16	35.90	63.5	46.5	53.7	112.9	37.9	64.5	47.7	54.6	113	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C2-525AXSP16	42.40	74	54.5	62.8	129.3	44.9	75.2	56.1	64	129.6	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C2-532AXSP16	39.40	69.9	51.1	59.3	123.3	41.8	71	52.6	60.3	123.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C3-425AXSP16	45.40	79.7	58.6	67.6	137.5	48.5	81	60.3	68.9	137.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C3-632AXSP16	43.10	76.7	56	64.8	133.7	46.1	78	57.8	66.1	133.9	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C3-625AXSP16	39.20	68.3	50.3	57.8	120.8	41.3	69.3	51.6	58.9	120.9	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C3-432AXSP16	35.90	63.5	46.5	53.7	112.9	37.9	64.5	47.7	54.6	113	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C3-525AXSP16	42.40	74	54.5	62.8	129.3	44.9	75.2	56.1	64	129.6	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C3-532AXSP16	39.40	69.9	51.1	59.3	123.3	41.8	71	52.6	60.3	123.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C3-625AXSP16	45.40	79.7	58.6	67.6	137.5	48.5	81	60.3	68.9	137.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C3-632AXSP16	43.10	76.7	56	64.8	133.7	46.1	78	57.8	66.1	133.9	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C4-425AXSP16	39.20	68.3	50.3	57.8	120.8	41.3	69.3	51.6	58.9	120.9	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C4-432AXSP16	35.90	63.5	46.5	53.7	112.9	37.9	64.5	47.7	54.6	113	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C4-525AXSP16	42.40	74	54.5	62.8	129.3	44.9	75.2	56.1	64	129.6	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C4-532AXSP16	39.40	69.9	51.1	59.3	123.3	41.8	71	52.6	60.3	123.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C4-625AXSP16	45.40	79.7	58.6	67.6	137.5	48.5	81	60.3	68.9	137.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C4-632AXSP16	43.10	76.7	56	64.8	133.7	46.1	78	57.8	66.1	133.9	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C5-425AXSP16	39.20	68.3	50.3	57.8	120.8	41.3	69.3	51.6	58.9	120.9	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C5-432AXSP16	35.90	63.5	46.5	53.7	112.9	37.9	64.5	47.7	54.6	113	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C5-525AXSP16	42.40	74	54.5	62.8	129.3	44.9	75.2	56.1	64	129.6	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C5-532AXSP16	39.40	69.9	51.1	59.3	123.3	41.8	71	52.6	60.3	123.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C5-625AXSP16	45.40	79.7	58.6	67.6	137.5	48.5	81	60.3	68.9	137.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C5-632AXSP16	43.10	76.7	56	64.8	133.7	46.1	78	57.8	66.1	133.9	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C8-425AXSP16	39.20	68.3	50.3	57.8	120.8	41.3	69.3	51.6	58.9	120.9	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C8-432AXSP16	35.90	63.5	46.5	53.7	112.9	37.9	64.5	47.7	54.6	113	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C8-525AXSP16	42.40	74	54.5	62.8	129.3	44.9	75.2	56.1	64	129.6	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C8-532AXSP16	39.40	69.9	51.1	59.3	123.3	41.8	71	52.6	60.3	123.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C8-625AXSP16	45.40	79.7	58.6	67.6	137.5	48.5	81	60.3	68.9	137.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C8-632AXSP16	43.10	76.7	56	64.8	133.7	46.1	78	57.8	66.1	133.9	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550C9-425AXSP16	39.20	68.3	50.3	57.8	120.8	41.3	69.3	51.6	58.9	120.9	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C9-432AXSP16	35.90	63.5	46.5	53.7	112.9	37.9	64.5	47.7	54.6	113	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550C9-525AXSP16	42.40	74	54.5	62.8	129.3	44.9	75.2	56.1	64	129.6	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C9-532AXSP16	39.40	69.9	51.1	59.3	123.3	41.8	71	52.6	60.3	123.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550C9-625AXSP16	45.40	79.7	58.6	67.6	137.5	48.5	81	60.3	68.9	137.7	113	21.4	2"	90	14.1</				

EAW-FD15S1ZB550K9-632AXSP16	41.30	73.8	53.7	62.2	128.3	44.2	74.9	55.3	63.4	128.2	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550R3-425AXSP16	38.10	66.6	49.1	56.4	117.6	40.2	67.7	50.3	57.4	117.8	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550R3-432AXSP16	35.00	62	45.4	52.5	110.3	37	63	46.6	53.4	110.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB550R3-525AXSP16	41.40	72.5	53.3	61.5	126.5	43.8	73.5	54.8	62.6	126.5	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550R3-532AXSP16	38.40	68.3	49.9	57.9	120.4	40.9	69.5	51.3	58.9	120.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB550R3-625AXSP16	44.60	78.2	57.4	66.2	134.8	47.5	79.4	59.1	67.5	134.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB550R3-632AXSP16	42.10	75.2	54.8	63.5	130.8	45	76.4	56.4	64.7	130.7	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K2-425AXSP16	39.60	69.1	50.8	58.5	122	41.7	70.2	52.1	59.5	122.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K2-432AXSP16	36.30	64.3	47.1	54.3	114.2	38.4	65.3	48.4	55.4	114.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K2-525AXSP16	42.90	74.8	55.2	63.5	131	45.4	76.1	56.7	64.7	131.1	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K2-532AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K2-625AXSP16	46.20	80.7	59.4	68.5	139.4	49.2	82	61.2	69.8	139.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K2-632AXSP16	43.70	77.7	56.6	65.6	135.3	46.6	78.9	58.4	66.9	135.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K3-425AXSP16	39.60	69.1	50.8	58.5	122	41.7	70.2	52.1	59.5	122.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K3-432AXSP16	36.30	64.3	47.1	54.3	114.2	38.4	65.3	48.4	55.4	114.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K3-525AXSP16	42.90	74.8	55.2	63.5	131	45.4	76.1	56.7	64.7	131.1	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K3-532AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K3-625AXSP16	46.20	80.7	59.4	68.5	139.4	49.2	82	61.2	69.8	139.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K3-632AXSP16	43.70	77.7	56.6	65.6	135.3	46.6	78.9	58.4	66.9	135.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K4-425AXSP16	39.60	69.1	50.8	58.5	122	41.7	70.2	52.1	59.5	122.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K4-432AXSP16	36.30	64.3	47.1	54.3	114.2	38.4	65.3	48.4	55.4	114.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K4-525AXSP16	42.90	74.8	55.2	63.5	131	45.4	76.1	56.7	64.7	131.1	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K4-532AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K4-625AXSP16	46.20	80.7	59.4	68.5	139.4	49.2	82	61.2	69.8	139.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K4-632AXSP16	43.70	77.7	56.6	65.6	135.3	46.6	78.9	58.4	66.9	135.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K4-632AXSP16	39.60	69.1	50.8	58.5	122	41.7	70.2	52.1	59.5	122.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K4-632AXSP16	36.30	64.3	47.1	54.3	114.2	38.4	65.3	48.4	55.4	114.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K5-425AXSP16	42.90	74.8	55.2	63.5	131	45.4	76.1	56.7	64.7	131.1	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K5-525AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K5-532AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K5-625AXSP16	46.20	80.7	59.4	68.5	139.4	49.2	82	61.2	69.8	139.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K5-632AXSP16	43.70	77.7	56.6	65.6	135.3	46.6	78.9	58.4	66.9	135.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K5-632AXSP16	39.60	69.1	50.8	58.5	122	41.7	70.2	52.1	59.5	122.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K5-632AXSP16	36.30	64.3	47.1	54.3	114.2	38.4	65.3	48.4	55.4	114.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K5-632AXSP16	42.90	74.8	55.2	63.5	131	45.4	76.1	56.7	64.7	131.1	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K5-632AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K5-632AXSP16	46.20	80.7	59.4	68.5	139.4	49.2	82	61.2	69.8	139.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K5-632AXSP16	43.70	77.7	56.6	65.6	135.3	46.6	78.9	58.4	66.9	135.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K9-425AXSP16	39.60	69.1	50.8	58.5	122	41.7	70.2	52.1	59.5	122.2	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K9-432AXSP16	36.30	64.3	47.1	54.3	114.2	38.4	65.3	48.4	55.4	114.5	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750K9-525AXSP16	42.90	74.8	55.2	63.5	131	45.4	76.1	56.7	64.7	131.1	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K9-532AXSP16	39.90	70.8	51.8	60	124.7	42.4	71.9	53.2	61.1	124.8	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750K9-625AXSP16	46.20	80.7	59.4	68.5	139.4	49.2	82	61.2	69.8	139.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750K9-632AXSP16	43.70	77.7	56.6	65.6	135.3	46.6	78.9	58.4	66.9	135.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750R3-425AXSP16	38.80	67.7	49.8	57.3	119.6	40.9	68.8	51.1	58.3	119.7	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750R3-432AXSP16	35.60	63	46.1	53.3	112	37.6	64	47.4	54.2	112.3	73	18.5	2"	59	14.9	1-1/2"	88	25.9	2"
EAW-FD15S1ZB750R3-525AXSP16	41.90	73.4	54	62.3	128.2	44.4	74.5	55.5	63.4	128.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750R3-532AXSP16	39.00	69.4	50.7	58.8	122.3	41.5	70.5	52.2	59.9	122.3	90	19.6	2"	72	12.9	2"	108	27.5	2"
EAW-FD15S1ZB750R3-625AXSP16	45.10	79.1	58.1	67	136.4	48	80.2	59.8	68.3	136.4	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZB750R3-632AXSP16	42.70	76.1	55.4	64.2	132.4	45.6	77.4	57.2	65.5	132.5	113	21.4	2"	90	14.1	2"	135	24.2	3"
EAW-FD15S1ZK370C2-425AXSP16	39.30	67	49.8	57	117	41	67.7	50.7	57.6	116.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK370C2-432AXSP16	36.10	62.5	46.1	53.1	109.9	37.7	63.2	47.1	53.7	109.6	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK370C2-525AXSP16	42.60	72.7	54	61.9	125.4	44.6	73.4	55.1	62.7	125	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK370C2-532AXSP16	39.80	68.9	50.8	58.6	120	41.8	69.7	52	59.3	119.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK370C2-625AXSP16	45.80	78.1	58	66.4	129.9	48.2	79	59.3	67.4	132.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK370C2-632AXSP16	43.60	75.5	55.6	64	129.9	46	76.4	56.9	64.9	129.4	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK370C4-425AXSP16	39.30	67	49.8	57	117	41	67.7	50.7	57.6	116.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK370C4-432AXSP16	36.10	62.5	46.1	53.1	109.9	37.7	63.2	47.1	53.7	109.6	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK370C4-525AXSP16	42.60	72.7	54	61.9	125.4	44.6	73.4	55.1	62.7	125	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK370C4-532AXSP16	39.80	68.9	50.8	58.6	120	41.8	69.7	52	59.3	119.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK370C4-625AXSP16	45.80	78.1	58	66.4	132.9	48.2	79	59.3	67.4	132.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK370C4-632AXSP16	43.60	75.5	55.6	64	129.9	46	76.4	56.9	64.9	129.4	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK370C5-425AXSP16	39.30	67	49.8	57	117	41	67.7	50.7	57.6	116.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK370C5-432AXSP16	36.10	62.5	46.1	53.1	109.9	37.7	63.2	47.1	53.7	109.6	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK370C5-525AXSP16	42.60	72.7	54																

EAW-FD1551ZK400B3-625AXSP16	43.80	74.9	55.4	63.5	127.2	46.2	75.6	56.8	64.5	126.9	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400B3-632AXSP16	41.90	72.6	53.4	61.5	124.7	44.2	73.4	54.7	62.4	124.4	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400C3-425AXSP16	39.30	67	49.8	57	117	41	67.7	50.7	57.6	116.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400C3-432AXSP16	36.10	62.5	46.1	53.1	109.9	37.7	63.2	47.1	53.7	109.6	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400C3-525AXSP16	42.60	72.7	54	61.9	125.4	44.6	73.4	55.1	62.7	125	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400C3-532AXSP16	39.80	68.9	50.8	58.6	120	41.8	69.7	52	59.3	119.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400C3-625AXSP16	45.80	78.1	58	66.4	132.9	48.2	79	59.3	67.4	132.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400C3-632AXSP16	43.60	75.5	55.6	64	129.9	46	76.4	56.9	64.9	129.4	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400C9-425AXSP16	39.30	67	49.8	57	117	41	67.7	50.7	57.6	116.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400C9-432AXSP16	36.10	62.5	46.1	53.1	109.9	37.7	63.2	47.1	53.7	109.6	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400C9-525AXSP16	42.60	72.7	54	61.9	125.4	44.6	73.4	55.1	62.7	125	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400C9-532AXSP16	39.80	68.9	50.8	58.6	120	41.8	69.7	52	59.3	119.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400C9-625AXSP16	45.80	78.1	58	66.4	132.9	48.2	79	59.3	67.4	132.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400C9-632AXSP16	43.60	75.5	55.6	64	129.9	46	76.4	56.9	64.9	129.4	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400K3-425AXSP16	38.00	64.9	48.2	55.2	113.1	39.6	65.5	49	55.8	112.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400K3-432AXSP16	34.90	60.5	44.5	51.3	106.1	36.5	61.1	45.5	51.9	105.7	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400K3-525AXSP16	41.30	70.5	52.4	60.1	121.7	43.2	71.2	53.4	60.7	121.1	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400K3-532AXSP16	38.50	66.7	49.2	56.7	116	40.4	67.4	50.2	57.4	115.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400K3-625AXSP16	44.60	76.2	56.5	64.8	129.7	46.9	76.9	57.7	65.6	129	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400K3-632AXSP16	42.20	73.3	54	62.1	126	44.6	74	55.2	62.9	125.3	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400K9-425AXSP16	38.00	64.9	48.2	55.2	113.1	39.6	65.5	49	55.8	112.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400K9-432AXSP16	34.90	60.5	44.5	51.3	106.1	36.5	61.1	45.5	51.9	105.7	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400K9-525AXSP16	41.30	70.5	52.4	60.1	121.7	43.2	71.2	53.4	60.7	121.1	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400K9-532AXSP16	38.50	66.7	49.2	56.7	116	40.4	67.4	50.2	57.4	115.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400K9-625AXSP16	44.60	76.2	56.5	64.8	129.7	46.9	76.9	57.7	65.6	129	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400K9-632AXSP16	42.20	73.3	54	62.1	126	44.6	74	55.2	62.9	125.3	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400R3-425AXSP16	38.50	65.7	48.8	55.8	114.8	40.1	66.4	49.7	56.5	114.3	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400R3-432AXSP16	35.40	61.3	45.2	52	107.5	37	61.9	46.1	52.6	107.2	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK400R3-525AXSP16	41.80	71.4	53	60.8	123.1	43.8	72.1	54	61.5	122.7	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400R3-532AXSP16	39.00	67.6	49.8	57.4	117.6	41	68.3	50.9	58.2	117.1	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK400R3-625AXSP16	45.30	77.2	57.2	65.5	131.2	47.5	77.8	58.5	66.3	130.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK400R3-632AXSP16	42.90	74.2	54.6	62.8	127.6	45.2	75	55.9	63.7	126.9	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550B3-425AXSP16	41.20	70.1	52	59.5	-	43	70.9	53	60.4	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550B3-432AXSP16	38.00	65.5	48.4	55.6	115.3	39.7	66.3	49.4	56.3	115.1	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550B3-525AXSP16	44.50	75.6	56.3	64.4	130.7	46.5	76.6	57.5	65.3	130.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550B3-532AXSP16	41.70	71.8	53.1	61.1	125.2	43.7	72.7	54.3	62	125.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550B3-625AXSP16	47.60	80.9	60.1	68.8	137.8	50.1	81.9	61.6	69.9	137.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550B3-632AXSP16	45.50	78.5	57.9	66.6	135.1	48	79.5	59.3	67.6	135	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C2-425AXSP16	43.90	74.4	55.1	63.2	-	45.7	75.4	56.2	64	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C2-432AXSP16	40.20	69.1	51.1	58.6	121.9	41.9	69.9	52	59.4	121.5	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C2-525AXSP16	47.80	81	60.3	69	140.5	49.9	82	61.5	69.9	140.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C2-532AXSP16	44.50	76.4	56.6	65	133.5	46.6	77.3	57.8	65.8	133.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C2-625AXSP16	51.70	87.5	65.2	74.8	149.7	54.3	88.5	66.7	75.8	149.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C2-632AXSP16	49.00	84.1	62.2	71.5	145.2	51.4	85.1	63.7	72.6	144.9	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C3-425AXSP16	43.90	74.4	55.1	63.2	-	45.7	75.4	56.2	64	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C3-432AXSP16	40.20	69.1	51.1	58.6	121.9	41.9	69.9	52	59.4	121.5	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C3-525AXSP16	47.80	81	60.3	69	140.5	49.9	82	61.5	69.9	140.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C3-532AXSP16	44.50	76.4	56.6	65	133.5	46.6	77.3	57.8	65.8	133.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C3-625AXSP16	51.70	87.5	65.2	74.8	149.7	54.3	88.5	66.7	75.8	149.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C3-632AXSP16	49.00	84.1	62.2	71.5	145.2	51.4	85.1	63.7	72.6	144.9	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C4-425AXSP16	43.90	74.4	55.1	63.2	-	45.7	75.4	56.2	64	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C4-432AXSP16	40.20	69.1	51.1	58.6	121.9	41.9	69.9	52	59.4	121.5	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C4-525AXSP16	47.80	81	60.3	69	140.5	49.9	82	61.5	69.9	140.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C4-532AXSP16	44.50	76.4	56.6	65	133.5	46.6	77.3	57.8	65.8	133.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C4-625AXSP16	51.70	87.5	65.2	74.8	149.7	54.3	88.5	66.7	75.8	149.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C4-632AXSP16	49.00	84.1	62.2	71.5	145.2	51.4	85.1	63.7	72.6	144.9	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C5-425AXSP16	43.90	74.4	55.1	63.2	-	45.7	75.4	56.2	64	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C5-432AXSP16	40.20	69.1	51.1	58.6	121.9	41.9	69.9	52	59.4	121.5	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C5-525AXSP16	47.80	81	60.3	69	140.5	49.9	82	61.5	69.9	140.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C5-532AXSP16	44.50	76.4	56.6	65	133.5	46.6	77.3	57.8	65.8	133.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD1551ZK550C5-625AXSP16	51.70	87.5	65.2	74.8	149.7	54.3	88.5	66.7	75.8	149.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C5-632AXSP16	49.00	84.1	62.2	71.5	145.2	51.4	85.1	63.7	72.6	144.9	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD1551ZK550C8-425AXSP16	43.90	74.4	55.1	63.2	-	45.7	75.4	56.2	64	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C8-432AXSP16	40.20	69.1	51.1	58.6	121.9	41.9	69.9	52	59.4	121.5	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD1551ZK550C8-525AXSP16	47.80	81	60.3	69	140.5	49.9	82	61.5	69.9	140.3	90	20.9	2"	72	13.8	2"	108	29.4	


EAW-FD15S1ZK550K8-532AXSP16	42.40	73.2	54	62.2	127.4	44.4	73.9	55.2	63	127.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK550K8-625AXSP16	49.40	83.8	62.4	71.5	143.1	51.8	84.7	63.7	72.4	142.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK550K8-632AXSP16	46.70	80.5	59.4	68.3	138.6	49.1	81.4	60.7	69.2	138.2	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK550K9-425AXSP16	41.90	71.2	52.8	60.4	-	43.6	72	53.8	61.2	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK550K9-432AXSP16	38.40	66.2	48.9	56.1	116.5	40.1	66.9	49.8	56.9	116.3	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK550K9-525AXSP16	45.60	77.5	57.7	65.9	134.1	47.6	78.3	58.8	66.8	133.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK550K9-532AXSP16	42.40	73.2	54	62.2	127.4	44.4	73.9	55.2	63	127.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK550K9-625AXSP16	49.40	83.8	62.4	71.5	143.1	51.8	84.7	63.7	72.4	142.7	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK550K9-632AXSP16	46.70	80.5	59.4	68.3	138.6	49.1	81.4	60.7	69.2	138.2	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK550R3-425AXSP16	42.80	72.7	53.8	61.7	-	44.5	73.5	54.9	62.5	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK550R3-432AXSP16	39.20	67.5	49.9	57.3	118.9	40.9	68.3	50.9	58	118.8	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK550R3-525AXSP16	46.60	79.1	58.9	67.3	136.7	48.7	79.9	60	68.2	136.6	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK550R3-632AXSP16	43.30	74.6	55.2	63.4	130.2	45.4	75.5	56.3	64.3	129.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK550R3-625AXSP16	50.50	85.6	63.7	73	146.1	52.9	86.4	65	73.9	145.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK550R3-632AXSP16	47.70	82.1	60.7	69.8	141.5	50.1	83.1	62	70.7	141.2	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750C4-425AXSP16	46.00	77.8	57.6	66	-	47.8	78.8	58.8	67	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750C4-432AXSP16	42.10	72.3	53.4	61.3	-	43.9	73.2	54.5	62.2	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750C4-525AXSP16	49.80	84.3	62.8	71.7	146.2	52.1	85.3	64	72.8	146.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750C4-532AXSP16	46.50	79.7	59.1	67.7	139.4	48.6	80.7	60.3	68.7	139.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750C4-625AXSP16	51.00	87.5	64.7	74.4	151.1	53.5	88.6	66.3	75.6	151	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750C5-425AXSP16	46.00	77.8	57.6	66	-	47.8	78.8	58.8	67	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750C5-432AXSP16	42.10	72.3	53.4	61.3	-	43.9	73.2	54.5	62.2	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750C5-525AXSP16	49.80	84.3	62.8	71.7	146.2	52.1	85.3	64	72.8	146.3	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750C5-532AXSP16	46.50	79.7	59.1	67.7	139.4	48.6	80.7	60.3	68.7	139.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K2-625AXSP16	51.00	87.5	64.7	74.4	151.1	53.5	88.6	66.3	75.6	151	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K2-425AXSP16	44.50	75.5	55.9	64.1	-	46.3	76.5	57	65	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K2-432AXSP16	40.90	70.2	51.9	59.5	-	42.6	71.1	52.9	60.3	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K2-525AXSP16	48.40	82	61.1	69.8	142.1	50.6	83	62.3	70.7	141.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K2-532AXSP16	45.10	77.4	57.3	65.8	135.3	47.2	78.4	58.5	66.7	135	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K2-625AXSP16	52.40	88.6	66.1	75.7	151.7	55	89.7	67.6	76.8	151.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K2-632AXSP16	49.60	85.1	63.1	72.5	147.1	52.1	86.2	64.5	73.6	146.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K3-425AXSP16	44.50	75.5	55.9	64.1	-	46.3	76.5	57	65	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K3-432AXSP16	40.90	70.2	51.9	59.5	-	42.6	71.1	52.9	60.3	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K3-525AXSP16	48.40	82	61.1	69.8	142.1	50.6	83	62.3	70.7	141.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K3-532AXSP16	45.10	77.4	57.3	65.8	135.3	47.2	78.4	58.5	66.7	135	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K3-625AXSP16	52.40	88.6	66.1	75.7	151.7	55	89.7	67.6	76.8	151.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K3-632AXSP16	49.60	85.1	63.1	72.5	147.1	52.1	86.2	64.5	73.6	146.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K4-425AXSP16	44.50	75.5	55.9	64.1	-	46.3	76.5	57	65	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K4-432AXSP16	40.90	70.2	51.9	59.5	-	42.6	71.1	52.9	60.3	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K4-525AXSP16	48.40	82	61.1	69.8	142.1	50.6	83	62.3	70.7	141.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K4-532AXSP16	45.10	77.4	57.3	65.8	135.3	47.2	78.4	58.5	66.7	135	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K4-625AXSP16	52.40	88.6	66.1	75.7	151.7	55	89.7	67.6	76.8	151.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K4-632AXSP16	49.60	85.1	63.1	72.5	147.1	52.1	86.2	64.5	73.6	146.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K5-425AXSP16	44.50	75.5	55.9	64.1	-	46.3	76.5	57	65	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K5-432AXSP16	40.90	70.2	51.9	59.5	-	42.6	71.1	52.9	60.3	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K5-525AXSP16	48.40	82	61.1	69.8	142.1	50.6	83	62.3	70.7	141.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K5-532AXSP16	45.10	77.4	57.3	65.8	135.3	47.2	78.4	58.5	66.7	135	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K5-625AXSP16	52.40	88.6	66.1	75.7	151.7	55	89.7	67.6	76.8	151.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K5-632AXSP16	49.60	85.1	63.1	72.5	147.1	52.1	86.2	64.5	73.6	146.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K8-425AXSP16	44.50	75.5	55.9	64.1	-	46.3	76.5	57	65	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K8-432AXSP16	40.90	70.2	51.9	59.5	-	42.6	71.1	52.9	60.3	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K8-525AXSP16	48.40	82	61.1	69.8	142.1	50.6	83	62.3	70.7	141.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K8-532AXSP16	45.10	77.4	57.3	65.8	135.3	47.2	78.4	58.5	66.7	135	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K8-625AXSP16	52.40	88.6	66.1	75.7	151.7	55	89.7	67.6	76.8	151.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K8-632AXSP16	49.60	85.1	63.1	72.5	147.1	52.1	86.2	64.5	73.6	146.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K9-425AXSP16	44.50	75.5	55.9	64.1	-	46.3	76.5	57	65	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K9-432AXSP16	40.90	70.2	51.9	59.5	-	42.6	71.1	52.9	60.3	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750K9-525AXSP16	48.40	82	61.1	69.8	142.1	50.6	83	62.3	70.7	141.9	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K9-532AXSP16	45.10	77.4	57.3	65.8	135.3	47.2	78.4	58.5	66.7	135	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750K9-625AXSP16	52.40	88.6	66.1	75.7	151.7	55	89.7	67.6	76.8	151.5	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750K9-632AXSP16	49.60	85.1	63.1	72.5	147.1	52.1	86.2	64.5	73.6	146.8	113	22.8	2"	90	15	2"	135	26.1	3"
EAW-FD15S1ZK750R3-425AXSP16	43.60	73.9	54.8	62.8	-	45.4	74.8	55.9	63.7	-	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750R3-432AXSP16	40.00	68.8	50.9	58.4	121.4	41.8	69.7	51.9	59.1	121.1	73	19.8	2"	59	15.7	1-1/2"	88	27.8	2"
EAW-FD15S1ZK750R3-525AXSP16	47.40	80.3	59.8	68.3	139	49.4	81.2	60.9	69.2	138.8	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750R3-532AXSP16	44.10	75.8	56.1	64.5	132.3	46.2	76.7	57.4	65.3	132.2	90	20.9	2"	72	13.8	2"	108	29.4	2"
EAW-FD15S1ZK750R3-625AXSP16	51.20	86.8	64.6	74	148.1</														

EAW-FD1552PB370K4-625AXSP12	86.00	136.7	103.9	117.2	-	87.8	137.2	105	117.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB370K4-632AXSP12	81.90	132	99.9	112.9	223.2	83.9	132.6	100.9	113.6	222	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB370K5-425AXSP12	73.50	119.5	89.7	102	-	75	120	90.7	102.5	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB370K5-432AXSP12	68.30	111.6	83.7	95.2	-	69.7	112.2	84.5	95.8	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB370K5-525AXSP12	81.00	130.1	98.3	111.3	-	82.7	130.8	99.3	111.9	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB370K5-532AXSP12	76.30	123.6	93.2	105.6	-	78	124.3	94	106.2	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB370K5-625AXSP12	86.00	136.7	103.9	117.2	-	87.8	137.2	105	117.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB370K5-632AXSP12	81.90	132	99.9	112.9	223.2	83.9	132.6	100.9	113.6	222	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB370K8-425AXSP12	73.50	119.5	89.7	102	-	75	120	90.7	102.5	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB370K8-432AXSP12	68.30	111.6	83.7	95.2	-	69.7	112.2	84.5	95.8	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB370K8-525AXSP12	81.00	130.1	98.3	111.3	-	82.7	130.8	99.3	111.9	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB370K8-532AXSP12	76.30	123.6	93.2	105.6	-	78	124.3	94	106.2	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB370K8-625AXSP12	86.00	136.7	103.9	117.2	-	87.8	137.2	105	117.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB370K8-632AXSP12	81.90	132	99.9	112.9	223.2	83.9	132.6	100.9	113.6	222	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400B3-425AXSP12	72.40	117.7	88.4	100.4	-	74.1	118.5	89.5	101.3	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400B3-432AXSP12	67.70	110.7	83	94.4	-	69.3	111.6	84	95.2	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400B3-525AXSP08	-	-	-	-	-	-	-	-	-	-	169	16.3	3"	135	10.7	3"	203	22.8	3"
EAW-FD1552PB400B3-532AXSP12	75.00	121.3	91.4	103.7	-	76.7	122.2	92.5	104.5	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1552PB400B3-632AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1552PB400C3-425AXSP08	65.80	115.7	84.9	97.9	203.8	69.6	117.5	87.3	99.8	204	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB400C3-432AXSP12	70.00	114.6	85.8	97.7	-	71.6	115.4	86.8	98.4	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400C3-525AXSP12	82.10	131.7	99.6	112.8	-	84	132.8	100.9	113.8	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400C3-532AXSP12	77.90	126.1	95	107.7	-	79.5	127	96.1	108.7	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400C3-625AXSP12	86.10	136.9	104.3	117.6	-	88.3	138	105.5	118.6	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400C3-632AXSP12	83.00	133.6	101	114.4	-	85.1	134.4	102.4	115.3	225.4	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400C9-425AXSP08	65.80	115.7	84.9	97.9	203.8	69.6	117.5	87.3	99.8	204	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB400C9-432AXSP12	70.00	114.6	85.8	97.7	-	71.6	115.4	86.8	98.4	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400C9-525AXSP12	82.10	131.7	99.6	112.8	-	84	132.8	100.9	113.8	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400C9-532AXSP12	77.90	126.1	95	107.7	-	79.5	127	96.1	108.7	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400C9-625AXSP12	86.10	136.9	104.3	117.6	-	88.3	138	105.5	118.6	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400C9-632AXSP12	83.00	133.6	101	114.4	-	85.1	134.4	102.4	115.3	225.4	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400K3-425AXSP12	73.50	119.5	89.7	102	-	75	120	90.7	102.5	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400K3-432AXSP12	68.30	111.6	83.7	95.2	-	69.7	112.2	84.5	95.8	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400K3-525AXSP12	81.00	130.1	98.3	111.3	-	82.7	130.8	99.3	111.9	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400K3-532AXSP12	76.30	123.6	93.2	105.6	-	78	124.3	94	106.2	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400K3-625AXSP12	86.00	136.7	103.9	117.2	-	87.8	137.2	105	117.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400K3-632AXSP12	81.90	132	99.9	112.9	223.2	83.9	132.6	100.9	113.6	222	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400K9-425AXSP12	73.50	119.5	89.7	102	-	75	120	90.7	102.5	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400K9-432AXSP12	68.30	111.6	83.7	95.2	-	69.7	112.2	84.5	95.8	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400K9-525AXSP12	81.00	130.1	98.3	111.3	-	82.7	130.8	99.3	111.9	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400K9-532AXSP12	76.30	123.6	93.2	105.6	-	78	124.3	94	106.2	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400K9-625AXSP12	86.00	136.7	103.9	117.2	-	87.8	137.2	105	117.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400K9-632AXSP12	81.90	132	99.9	112.9	223.2	83.9	132.6	100.9	113.6	222	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400R3-425AXSP12	74.20	120.8	90.7	103	-	75.8	121.3	91.6	103.8	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400R3-432AXSP12	68.90	112.9	84.6	96.2	-	70.4	113.5	85.5	96.8	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB400R3-525AXSP12	81.80	131.2	99.3	112.4	-	83.4	132	100.3	113.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400R3-532AXSP12	77.10	125	94.1	106.8	-	78.7	125.6	95	107.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB400R3-625AXSP12	86.70	137.9	104.9	118.3	-	88.6	138.5	105.9	119	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB400R3-632AXSP12	82.80	133.3	100.8	114	225.2	84.7	133.8	101.9	114.8	224.4	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB550B3-425AXSP08	68.10	119.2	87.8	101	210.5	72.1	121.4	90.3	103.1	211.3	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB550B3-432AXSP12	72.40	118.7	88.8	101.1	-	74.1	119.7	90	102	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD1552PB550B3-525AXSP08	-	-	-	-	-	-	-	-	-	-	169	16.3	3"	135	10.7	3"	203	22.8	3"
EAW-FD1552PB550B3-532AXSP12	-	-	-	-	-	82.1	130.9	99.1	112.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB550B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1552PB550B3-632AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1552PB550C2-425AXSP08	73.40	127.9	94.2	108.2	-	77.5	130.1	96.7	110.4	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB550C2-432AXSP08	67.50	119.3	87.4	100.9	212	71.4	121.4	89.9	102.8	212.7	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB550C2-525AXSP12	90.90	146.7	110.6	125.3	-	93	147.7	112.1	126.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB550C2-532AXSP12	85.80	139.5	104.9	119	-	87.8	140.5	106.2	120	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB550C2-632AXSP12	-	-	-	-	-	94.3	149.4	113.5	127.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB550C3-425AXSP08	73.40	127.9	94.2	108.2	-	77.5	130.1	96.7	110.4	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB550C3-432AXSP08	67.50	119.3	87.4	100.9	212	71.4	121.4	89.9	102.8	212.7	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD1552PB550C3-525AXSP12	90.90	146.7	110.6	125.3	-	93	147.7	112.1	126.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB550C3-532AXSP12	85.80	139.5	104.9	119	-	87.8	140.5	106.2	120	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD1552PB550C3-625AXSP08	-	-	-	-	-	-	-	-	-	-	203	17.2	3"	162	11.3	3"	244	24.2	3"
EAW-FD1552PB550C3-632AXSP12	-	-	-	-	-	94.3	149.4	113.5	127.9	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD1552PB550C4-425AXSP08	73.40	127.9	94.2	108.2	-	77.5	130.1	96.7	110.4	-	135	15.5	3"	108	14	2"	162	21.7	3"

EAW-FD15S2PB550K4-432AXSP12	74.00	121.4	90.7	103.4	-	75.6	122.1	91.8	104.2	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD15S2PB550K4-525AXSP12	88.00	141.7	106.9	121.2	-	89.8	142.5	108.2	122.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K4-532AXSP12	82.80	134.5	101.2	114.9	-	84.7	135.4	102.3	115.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K4-625AXSP12	93.50	148.8	113.2	127.6	-	95.5	149.7	114.3	128.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K4-632AXSP12	89.30	143.6	108.4	122.8	-	91.3	144.3	109.6	123.6	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K5-425AXSP08	70.40	122.9	90.6	104.1	217.1	74.3	125	92.9	106.1	217.6	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB550K5-432AXSP12	74.00	121.4	90.7	103.4	-	75.6	122.1	91.8	104.2	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD15S2PB550K5-525AXSP12	88.00	141.7	106.9	121.2	-	89.8	142.5	108.2	122.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K5-532AXSP12	82.80	134.5	101.2	114.9	-	84.7	135.4	102.3	115.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K5-625AXSP12	93.50	148.8	113.2	127.6	-	95.5	149.7	114.3	128.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K5-632AXSP12	89.30	143.6	108.4	122.8	-	91.3	144.3	109.6	123.6	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K8-425AXSP08	70.40	122.9	90.6	104.1	217.1	74.3	125	92.9	106.1	217.6	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB550K8-432AXSP12	74.00	121.4	90.7	103.4	-	75.6	122.1	91.8	104.2	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD15S2PB550K8-525AXSP12	88.00	141.7	106.9	121.2	-	89.8	142.5	108.2	122.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K8-532AXSP12	82.80	134.5	101.2	114.9	-	84.7	135.4	102.3	115.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K8-625AXSP12	93.50	148.8	113.2	127.6	-	95.5	149.7	114.3	128.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K8-632AXSP12	89.30	143.6	108.4	122.8	-	91.3	144.3	109.6	123.6	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K9-425AXSP12	74.00	121.4	90.7	103.4	-	75.6	122.1	91.8	104.2	-	90	24.4	2"	72	16.1	2"	108	34.3	2"
EAW-FD15S2PB550K9-432AXSP12	88.00	141.7	106.9	121.2	-	89.8	142.5	108.2	122.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K9-532AXSP12	82.80	134.5	101.2	114.9	-	84.7	135.4	102.3	115.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550K9-625AXSP12	93.50	148.8	113.2	127.6	-	95.5	149.7	114.3	128.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550K9-632AXSP12	89.30	143.6	108.4	122.8	-	91.3	144.3	109.6	123.6	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550R3-425AXSP08	71.70	125.3	92.2	106.1	221.2	75.7	127.3	94.6	108.1	221.5	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB550R3-432AXSP08	65.80	116.7	85.4	98.7	207.6	69.108	118.7	87.8	100.5	207.6	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB550R3-525AXSP12	89.40	144.1	108.8	123.1	-	91.4	145	110.1	124.1	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550R3-532AXSP12	84.20	136.7	102.9	116.7	-	86.1	137.8	104.1	117.6	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB550R3-625AXSP12	95.10	151.5	115.1	129.8	-	97.2	152.4	116.3	130.8	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB550R3-632AXSP12	90.70	145.9	110.3	124.9	-	92.7	146.7	111.6	125.8	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K2-425AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K2-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K2-525AXSP12	92.00	148.4	112.1	127	-	94.1	149.6	113.5	128	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K2-532AXSP12	86.70	141	105.9	120.5	-	88.8	142.1	107.3	121.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K2-625AXSP12	97.80	155.8	118.3	133.5	-	100	157	119.7	134.7	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K3-425AXSP12	93.30	150.3	113.5	128.4	-	95.5	151.4	114.8	129.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K3-432AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K3-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K3-525AXSP12	92.00	148.4	112.1	127	-	94.1	149.6	113.5	128	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K3-532AXSP12	86.70	141	105.9	120.5	-	88.8	142.1	107.3	121.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K3-625AXSP12	97.80	155.8	118.3	133.5	-	100	157	119.7	134.7	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K3-632AXSP12	93.30	150.3	113.5	128.4	-	95.5	151.4	114.8	129.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K4-425AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K4-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K4-525AXSP12	92.00	148.4	112.1	127	-	94.1	149.6	113.5	128	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K4-532AXSP12	86.70	141	105.9	120.5	-	88.8	142.1	107.3	121.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K4-625AXSP12	97.80	155.8	118.3	133.5	-	100	157	119.7	134.7	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K4-632AXSP12	93.30	150.3	113.5	128.4	-	95.5	151.4	114.8	129.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K5-425AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K5-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K5-525AXSP12	92.00	148.4	112.1	127	-	94.1	149.6	113.5	128	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K5-532AXSP12	86.70	141	105.9	120.5	-	88.8	142.1	107.3	121.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K5-625AXSP12	97.80	155.8	118.3	133.5	-	100	157	119.7	134.7	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K5-632AXSP12	93.30	150.3	113.5	128.4	-	95.5	151.4	114.8	129.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K8-425AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K8-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K8-525AXSP12	92.00	148.4	112.1	127	-	94.1	149.6	113.5	128	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K8-532AXSP12	86.70	141	105.9	120.5	-	88.8	142.1	107.3	121.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K8-625AXSP12	97.80	155.8	118.3	133.5	-	100	157	119.7	134.7	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K8-632AXSP12	93.30	150.3	113.5	128.4	-	95.5	151.4	114.8	129.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K9-425AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K9-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750K9-525AXSP12	92.00	148.4	112.1	127	-	94.1	149.6	113.5	128	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K9-532AXSP12	86.70	141	105.9	120.5	-	88.8	142.1	107.3	121.3	-	113	26.2	2"	90	17.3	2"	135	31	3"
EAW-FD15S2PB750K9-625AXSP12	97.80	155.8	118.3	133.5	-	100	157	119.7	134.7	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750K9-632AXSP12	93.30	150.3	113.5	128.4	-	95.5	151.4	114.8	129.5	-	135	22.5	3"	108	18.7	2"	162	31.6	3"
EAW-FD15S2PB750R3-425AXSP08	74.20	129.3	95.2	109.5	-	78.4	131.6	97.7	111.7	-	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750R3-432AXSP08	68.20	120.6	88.4	101.9	214.4	72.2	122.7	90.8	104	215.1	135	15.5	3"	108	14	2"	162	21.7	3"
EAW-FD15S2PB750R3-525AXSP12	90.30	145.6	109.9	124.5	-	92.3	146.7												

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1552ZB370K4-425AXSP12	79.40	128.9	96.8	109.9	-	81.1	129.5	97.9	110.6	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552ZB370K4-432AXSP12	73.70	120.6	90.2	102.7	-	75.2	121	91.1	103.2	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552ZB370K4-525AXSP12	86.50	138.9	105	118.9	-	88.2	139.4	106	119.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552ZB370K4-532AXSP12	81.30	131.8	99.2	112.6	-	83	132.2	100.2	113.2	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552ZB370K4-625AXSP12	93.10	148.1	112.8	127.2	247.7	95.1	148.5	113.7	127.7	246.1	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552ZB370K4-632AXSP12	88.60	142.9	108.1	122.4	241.3	90.7	143.3	109.2	122.9	239.5	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552ZB370K5-425AXSP12	79.40	128.9	96.8	109.9	-	81.1	129.5	97.9	110.6	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552ZB370K5-432AXSP12	73.70	120.6	90.2	102.7	-	75.2	121	91.1	103.2	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552ZB370K5-525AXSP12	86.50	138.9	105	118.9	-	88.2	139.4	106	119.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552ZB370K5-532AXSP12	81.30	131.8	99.2	112.6	-	83	132.2	100.2	113.2	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552ZB370K5-625AXSP12	93.10	148.1	112.8	127.2	247.7	95.1	148.5	113.7	127.7	246.1	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552ZB370K5-632AXSP12	88.60	142.9	108.1	122.4	241.3	90.7	143.3	109.2	122.9	239.5	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552ZB370K8-425AXSP12	79.40	128.9	96.8	109.9	-	81.1	129.5	97.9	110.6	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552ZB370K8-432AXSP12	73.70	120.6	90.2	102.7	-	75.2	121	91.1	103.2	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552ZB370K8-525AXSP12	86.50	138.9	105	118.9	-	88.2	139.4	106	119.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552ZB370K8-532AXSP12	81.30	131.8	99.2	112.6	-	83	132.2	100.2	113.2	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552ZB370K8-625AXSP12	93.10	148.1	112.8	127.2	247.7	95.1	148.5	113.7	127.7	246.1	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552ZB370K8-632AXSP12	88.60	142.9	108.1	122.4	241.3	90.7	143.3	109.2	122.9	239.5	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B40083-425AXSP12	78.90	128	96.3	109.3	-	80.6	128.8	97.4	110	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B40083-432AXSP12	73.60	120.3	90.1	102.5	-	75.1	120.9	91.1	103.2	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B40083-525AXSP12	85.10	136.4	103.2	116.8	-	87	137.3	104.4	117.6	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B40083-532AXSP12	80.60	130.5	98.3	111.6	-	82.4	131.3	99.5	112.4	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B40083-625AXSP08	-	-	-	-	-	-	-	-	-	-	225	18	3"	180	11.8	3"	270	21.5	4"
EAW-FD1552B40083-632AXSP12	87.00	140.2	106.3	120.1	236.5	89.2	141	107.4	121	235.6	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400C3-425AXSP12	81.60	132.7	99.7	113.2	-	83.4	133.5	100.8	114.1	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400C3-432AXSP12	75.90	124.1	93	105.9	-	77.5	124.7	94	106.5	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400C3-525AXSP12	88.40	142.1	107.4	121.6	-	90.4	142.8	108.5	122.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400C3-532AXSP12	83.60	135.5	101.9	115.8	-	85.3	136.2	103.1	116.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400C3-625AXSP12	94.50	150.3	114.3	129	251.8	96.8	151.1	115.6	129.9	250.9	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400C3-632AXSP12	90.70	146	110.5	125.1	246.7	92.8	146.8	111.8	125.8	245.6	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400C9-425AXSP12	81.60	132.7	99.7	113.2	-	83.4	133.5	100.8	114.1	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400C9-432AXSP12	75.90	124.1	93	105.9	-	77.5	124.7	94	106.5	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400C9-525AXSP12	88.40	142.1	107.4	121.6	-	90.4	142.8	108.5	122.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400C9-532AXSP12	83.60	135.5	101.9	115.8	-	85.3	136.2	103.1	116.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400C9-625AXSP12	94.50	150.3	114.3	129	251.8	96.8	151.1	115.6	129.9	250.9	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400C9-632AXSP12	90.70	146	110.5	125.1	246.7	92.8	146.8	111.8	125.8	245.6	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400K3-425AXSP12	79.40	128.9	96.8	109.9	-	81.1	129.5	97.9	110.6	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400K3-432AXSP12	73.70	120.6	90.2	102.7	-	75.2	121	91.1	103.2	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400K3-525AXSP12	86.50	138.9	105	118.9	-	88.2	139.4	106	119.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400K3-532AXSP12	81.30	131.8	99.2	112.6	-	83	132.2	100.2	113.2	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400K3-625AXSP12	93.10	148.1	112.8	127.2	247.7	95.1	148.5	113.7	127.7	246.1	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400K3-632AXSP12	88.60	142.9	108.1	122.4	241.3	90.7	143.3	109.2	122.9	239.5	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400K9-425AXSP12	79.40	128.9	96.8	109.9	-	81.1	129.5	97.9	110.6	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400K9-432AXSP12	73.70	120.6	90.2	102.7	-	75.2	121	91.1	103.2	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400K9-525AXSP12	86.50	138.9	105	118.9	-	88.2	139.4	106	119.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400K9-532AXSP12	81.30	131.8	99.2	112.6	-	83	132.2	100.2	113.2	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400K9-625AXSP12	93.10	148.1	112.8	127.2	247.7	95.1	148.5	113.7	127.7	246.1	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400K9-632AXSP12	88.60	142.9	108.1	122.4	241.3	90.7	143.3	109.2	122.9	239.5	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400R3-425AXSP12	80.30	130.3	98.2	111.2	-	82	130.9	99.1	111.9	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400R3-432AXSP12	74.60	121.9	91.3	104	-	76.1	122.4	92.3	104.6	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B400R3-525AXSP12	87.40	140.4	106.1	120.1	-	89.2	141	107.2	120.8	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400R3-532AXSP12	82.30	133.3	100.3	113.9	-	84.1	133.8	101.4	114.5	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B400R3-625AXSP12	94.00	149.5	113.8	128.3	250.5	96.1	150.2	114.9	129.1	249	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B400R3-632AXSP12	89.70	144.4	109.4	123.6	244	91.7	144.9	110.4	124.2	242.6	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B550B3-425AXSP08	74.40	130.6	96	110.6	230.2	78.7	132.6	98.7	112.6	230.4	152	15.9	3"	122	10.5	3"	183	22.3	3"
EAW-FD1552B550B3-432AXSP12	79.00	129.5	96.9	110.4	-	80.8	130.3	98	111.1	-	101	25.4	2"	81	16.7	2"	122	30.8	3"
EAW-FD1552B550B3-525AXSP12	91.40	146.8	110.9	125.7	-	93.4	147.9	112.4	126.8	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B550B3-532AXSP12	86.60	140.4	105.6	120	-	88.6	141.6	107	121	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B550B3-625AXSP08	-	-	-	-	-	-	-	-	-	-	225	18	3"	180	11.8	3"	270	21.5	4"
EAW-FD1552B550B3-632AXSP12	-	-	-	-	-	96	151.7	115.6	130.2	-	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B550C2-425AXSP08	79.70	139.3	102.5	117.9	246.1	84.1	141.4	105.2	120.1	246.2	152	15.9	3"	122	10.5	3"	183	22.3	3"
EAW-FD1552B550C2-432AXSP08	73.10	129.5	94.7	109.6	230.5	77.3	131.6	97.4	111.5	230.3	152	15.9	3"	122	10.5	3"	183	22.3	3"
EAW-FD1552B550C2-525AXSP12	98.30	158.4	119.4	135.3	-	100.4	159.4	120.8	136.4	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B550C2-532AXSP12	92.30	150	112.8	128.2	-	94.4	151	114.1	129	-	124	22.3	3"	99	18	2"	149	31.3	3"
EAW-FD1552B550C2-625AXSP12	105.70	168.2	127.9	144.3	-	108.1	169.4	129.3	145.5	-	152	22.9	3"	122	15.2	3"	183	32.2	3"
EAW-FD1552B550C2-632AXSP12	101.10	162.5	122.9	138.9	-	103.3	163.4	124.1	140.2	-									



EAW-FD1552ZK370C8-625AXSP12	104.30	163.9	125.1	140.8	-	106.1	164.2	126	141.3	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370C8-632AXSP12	100.10	158.8	120.7	136.1	-	101.7	159	121.4	136.5	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K2-425AXSP08	77.20	132.2	98	112.3	230.1	80.5	133.5	99.8	113.7	229.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK370K2-432AXSP12	80.00	129.7	97.5	110.7	-	81.3	129.9	98.2	111	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK370K2-525AXSP12	94.30	149.7	113.7	128.4	-	95.6	149.8	114.4	128.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K2-532AXSP12	88.70	142.1	107.5	121.7	-	90	142.3	108.1	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K2-625AXSP12	102.00	160	122.2	137.5	-	103.4	159.9	122.8	137.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K2-632AXSP12	97.10	154.1	117.3	132.2	-	98.7	154.1	117.9	132.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K4-425AXSP08	77.20	132.2	98	112.3	230.1	80.5	133.5	99.8	113.7	229.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK370K4-432AXSP12	80.00	129.7	97.5	110.7	-	81.3	129.9	98.2	111	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK370K4-525AXSP12	94.30	149.7	113.7	128.4	-	95.6	149.8	114.4	128.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K4-532AXSP12	88.70	142.1	107.5	121.7	-	90	142.3	108.1	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K4-625AXSP12	102.00	160	122.2	137.5	-	103.4	159.9	122.8	137.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K4-632AXSP12	97.10	154.1	117.3	132.2	-	98.7	154.1	117.9	132.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K5-425AXSP08	77.20	132.2	98	112.3	230.1	80.5	133.5	99.8	113.7	229.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK370K5-432AXSP12	80.00	129.7	97.5	110.7	-	81.3	129.9	98.2	111	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK370K5-525AXSP12	94.30	149.7	113.7	128.4	-	95.6	149.8	114.4	128.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K5-532AXSP12	88.70	142.1	107.5	121.7	-	90	142.3	108.1	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K5-625AXSP12	102.00	160	122.2	137.5	-	103.4	159.9	122.8	137.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K5-632AXSP12	97.10	154.1	117.3	132.2	-	98.7	154.1	117.9	132.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K8-425AXSP08	77.20	132.2	98	112.3	230.1	80.5	133.5	99.8	113.7	229.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK370K8-432AXSP12	80.00	129.7	97.5	110.7	-	81.3	129.9	98.2	111	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK370K8-525AXSP12	94.30	149.7	113.7	128.4	-	95.6	149.8	114.4	128.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K8-532AXSP12	88.70	142.1	107.5	121.7	-	90	142.3	108.1	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK370K8-625AXSP12	102.00	160	122.2	137.5	-	103.4	159.9	122.8	137.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK370K8-632AXSP12	97.10	154.1	117.3	132.2	-	98.7	154.1	117.9	132.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400B3-425AXSP08	77.10	132	97.9	112.1	230.2	80.6	133.6	99.9	113.8	229.6	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400B3-432AXSP12	80.40	130.1	98	111.2	-	81.7	130.5	98.5	111.5	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK400B3-525AXSP12	93.50	148.4	112.8	127.3	-	95.1	148.9	113.6	127.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400B3-532AXSP12	88.40	141.8	107.1	121.4	-	89.8	142	107.9	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400B3-625AXSP12	100.10	156.9	120	134.9	-	101.8	157.4	120.9	135.5	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400B3-632AXSP12	96.20	152.7	116.2	131	-	98	153	116.9	131.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400C3-425AXSP08	80.00	136.7	101.4	116	238.1	83.5	138.1	103.4	117.4	237.7	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400C3-432AXSP08	73.60	127.5	94	108.2	224	77	129	96	109.6	223.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400C3-525AXSP12	96.90	154.4	117.2	132.3	-	98.7	154.8	117.9	132.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400C3-532AXSP12	91.50	146.8	110.9	125.6	-	93	147	111.8	125.9	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400C3-625AXSP12	104.30	163.9	125.1	140.8	-	106.1	164.2	126	141.3	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400C3-632AXSP12	100.10	158.8	120.7	136.1	-	101.7	159	121.4	136.5	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400C9-425AXSP08	80.00	136.7	101.4	116	238.1	83.5	138.1	103.4	117.4	237.7	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400C9-432AXSP08	73.60	127.5	94	108.2	224	77	129	96	109.6	223.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400C9-525AXSP12	96.90	154.4	117.2	132.3	-	98.7	154.8	117.9	132.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400C9-532AXSP12	91.50	146.8	110.9	125.6	-	93	147	111.8	125.9	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400C9-625AXSP12	104.30	163.9	125.1	140.8	-	106.1	164.2	126	141.3	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400C9-632AXSP12	100.10	158.8	120.7	136.1	-	101.7	159	121.4	136.5	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400K3-425AXSP08	77.20	132.2	98	112.3	230.1	80.5	133.5	99.8	113.7	229.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400K3-432AXSP12	80.00	129.7	97.5	110.7	-	81.3	129.9	98.2	111	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK400K3-525AXSP12	94.30	149.7	113.7	128.4	-	95.6	149.8	114.4	128.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400K3-532AXSP12	88.70	142.1	107.5	121.7	-	90	142.3	108.1	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400K3-625AXSP12	102.00	160	122.2	137.5	-	103.4	159.9	122.8	137.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400K3-632AXSP12	97.10	154.1	117.3	132.2	-	98.7	154.1	117.9	132.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400K9-425AXSP08	77.20	132.2	98	112.3	230.1	80.5	133.5	99.8	113.7	229.4	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400K9-432AXSP12	80.00	129.7	97.5	110.7	-	81.3	129.9	98.2	111	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK400K9-525AXSP12	94.30	149.7	113.7	128.4	-	95.6	149.8	114.4	128.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400K9-532AXSP12	88.70	142.1	107.5	121.7	-	90	142.3	108.1	121.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400K9-625AXSP12	102.00	160	122.2	137.5	-	103.4	159.9	122.8	137.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400K9-632AXSP12	97.10	154.1	117.3	132.2	-	98.7	154.1	117.9	132.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400R3-425AXSP08	78.30	134.1	99.4	113.9	233.6	81.7	135.3	101.2	115.1	232.6	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK400R3-432AXSP12	81.20	131.4	98.9	112.3	-	82.4	131.7	99.5	112.4	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK400R3-625AXSP12	95.50	151.6	115.1	129.9	-	96.8	151.8	115.9	130.3	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400R3-532AXSP12	89.80	144	108.9	123.2	-	91.2	144.3	109.4	123.5	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK400R3-625AXSP12	103.10	161.8	123.6	139.1	-	104.6	162	124.4	139.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK400R3-632AXSP12	98.30	156	118.7	133.8	-	99.9	156.1	119.4	134	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK50B3-425AXSP08	83.90	142.9	106	121.3	249.5	87.5	144.7	108.1	123.1	249.3	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK50B3-432AXSP08	77.30	133.6	98.7	113.4	235.2	80.9	135.3	100.9	115	234.6	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK50B3-525AXSP12	100.90	160.6	121.8	137.7	-	102.6	161.4	122.9	138.3	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK50B3-532AXSP1																			

EAW-FD1552ZK550C9-532AXSP12	101.30	163	123	139.3	-	103	163.5	123.9	139.9	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550C9-625AXSP12	116.60	183.9	140.1	157.9	-	118.7	184.6	141.4	158.7	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550C9-632AXSP12	111.20	177.1	134.2	151.6	-	113.1	177.6	135.4	152.3	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K2-425AXSP08	85.20	145.1	107.7	123.2	253.7	88.8	146.7	109.7	124.8	253	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K2-432AXSP08	78.30	135.1	99.8	114.6	237.7	81.7	136.6	101.8	116	237.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K2-525AXSP12	103.20	164.6	124.7	141	-	105	165	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K2-532AXSP12	96.90	155.9	117.6	133.4	-	98.5	156.2	118.4	133.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K2-625AXSP12	111.80	176	134.3	151.2	-	113.6	176.4	135.1	151.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K2-632AXSP12	106.50	169.1	128.4	145.2	-	108.1	169.7	129.4	145.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K3-425AXSP08	85.20	145.1	107.7	123.2	253.7	88.8	146.7	109.7	124.8	253	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K3-432AXSP08	78.30	135.1	99.8	114.6	237.7	81.7	136.6	101.8	116	237.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K3-525AXSP12	103.20	164.6	124.7	141	-	105	165	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K3-532AXSP12	96.90	155.9	117.6	133.4	-	98.5	156.2	118.4	133.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K3-625AXSP12	111.80	176	134.3	151.2	-	113.6	176.4	135.1	151.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K3-632AXSP12	106.50	169.1	128.4	145.2	-	108.1	169.7	129.4	145.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K4-425AXSP08	85.20	145.1	107.7	123.2	253.7	88.8	146.7	109.7	124.8	253	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K4-432AXSP08	78.30	135.1	99.8	114.6	237.7	81.7	136.6	101.8	116	237.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K4-525AXSP12	103.20	164.6	124.7	141	-	105	165	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K4-532AXSP12	96.90	155.9	117.6	133.4	-	98.5	156.2	118.4	133.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K4-625AXSP12	111.80	176	134.3	151.2	-	113.6	176.4	135.1	151.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K4-632AXSP12	106.50	169.1	128.4	145.2	-	108.1	169.7	129.4	145.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K9-425AXSP08	85.20	145.1	107.7	123.2	253.7	88.8	146.7	109.7	124.8	253	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K9-432AXSP08	78.30	135.1	99.8	114.6	237.7	81.7	136.6	101.8	116	237.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550K9-525AXSP12	103.20	164.6	124.7	141	-	105	165	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K9-532AXSP12	96.90	155.9	117.6	133.4	-	98.5	156.2	118.4	133.8	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550K9-625AXSP12	111.80	176	134.3	151.2	-	113.6	176.4	135.1	151.6	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550K9-632AXSP12	106.50	169.1	128.4	145.2	-	108.1	169.7	129.4	145.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550R3-425AXSP08	87.10	148.2	109.8	125.7	-	90.7	149.9	112	127.5	-	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550R3-432AXSP08	79.90	137.8	101.9	116.9	242.7	83.5	139.5	103.9	118.5	242.3	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK550R3-532AXSP08	94.20	160.2	119.1	136.3	277	98.4	161.9	127.7	138	276.3	186	18.1	3"	149	11.9	3"	223	25.4	3"
EAW-FD1552ZK550R3-532AXSP12	98.90	159.1	120	136	-	100.5	159.5	120.8	136.4	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK550R3-625AXSP12	114.00	179.6	136.9	154.2	-	115.9	180.1	137.8	154.7	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK550R3-632AXSP12	108.60	172.6	131.2	148.1	-	110.3	173	132	148.4	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750C4-425AXSP12	103.10	166.7	125.5	142.4	-	104.9	167.7	126.6	143.1	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK750C4-432AXSP12	95.40	155.4	116.5	132.5	-	97.1	156	117.6	133.2	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK750C4-525AXSP12	112.10	179.4	135.6	153.6	-	114.2	180.3	136.9	154.3	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750C4-532AXSP12	105.40	170	128.2	145.1	-	107.3	170.6	129.2	146.1	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750C4-632AXSP12	115.50	184	139.5	157.6	-	117.5	184.7	140.8	158.5	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750C5-425AXSP12	103.10	166.7	125.5	142.4	-	104.9	167.7	126.6	143.1	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK750C5-432AXSP12	95.40	155.4	116.5	132.5	-	97.1	156	117.6	133.2	-	101	27.3	2"	81	18	2"	122	33.6	3"
EAW-FD1552ZK750C5-525AXSP12	112.10	179.4	135.6	153.6	-	114.2	180.3	136.9	154.3	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750C5-532AXSP12	105.40	170	128.2	145.1	-	107.3	170.6	129.2	146.1	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750C5-632AXSP12	115.50	184	139.5	157.6	-	117.5	184.7	140.8	158.5	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K2-425AXSP08	90.70	154	114.1	130.6	-	94.5	155.8	116.4	132.5	-	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K2-432AXSP08	83.40	143.4	106	121.6	252.8	86.9	145.2	108	123.2	252.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K2-525AXSP08	98.10	166.2	124	141.4	288	102.3	168.2	126.4	143.5	287.5	186	18.1	3"	149	11.9	3"	223	25.4	3"
EAW-FD1552ZK750K2-532AXSP12	102.40	164.9	124.6	141.1	-	104.2	165.6	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750K2-625AXSP12	118.10	186.3	141.9	159.9	-	120.2	186.8	143.2	160.7	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K2-632AXSP12	112.50	179.2	136	153.4	-	114.4	179.6	137.1	154.2	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K3-425AXSP08	90.70	154	114.1	130.6	-	94.5	155.8	116.4	132.5	-	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K3-432AXSP08	83.40	143.4	106	121.6	252.8	86.9	145.2	108	123.2	252.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K3-525AXSP08	98.10	166.2	124	141.4	288	102.3	168.2	126.4	143.5	287.5	186	18.1	3"	149	11.9	3"	223	25.4	3"
EAW-FD1552ZK750K3-532AXSP12	102.40	164.9	124.6	141.1	-	104.2	165.6	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750K3-625AXSP12	118.10	186.3	141.9	159.9	-	120.2	186.8	143.2	160.7	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K3-632AXSP12	112.50	179.2	136	153.4	-	114.4	179.6	137.1	154.2	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K4-425AXSP08	90.70	154	114.1	130.6	-	94.5	155.8	116.4	132.5	-	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K4-432AXSP08	83.40	143.4	106	121.6	252.8	86.9	145.2	108	123.2	252.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K4-525AXSP08	98.10	166.2	124	141.4	288	102.3	168.2	126.4	143.5	287.5	186	18.1	3"	149	11.9	3"	223	25.4	3"
EAW-FD1552ZK750K4-532AXSP12	102.40	164.9	124.6	141.1	-	104.2	165.6	125.6	141.6	-	124	24.3	3"	99	19.4	2"	149	34.1	3"
EAW-FD1552ZK750K4-625AXSP12	118.10	186.3	141.9	159.9	-	120.2	186.8	143.2	160.7	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K4-632AXSP12	112.50	179.2	136	153.4	-	114.4	179.6	137.1	154.2	-	152	24.9	3"	122	16.5	3"	183	35	3"
EAW-FD1552ZK750K5-425AXSP08	90.70	154	114.1	130.6	-	94.5	155.8	116.4	132.5	-	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K5-432AXSP08	83.40	143.4	106	121.6	252.8	86.9	145.2	108	123.2	252.2	152	17.2	3"	122	11.4	3"	183	24.2	3"
EAW-FD1552ZK750K5-525AXSP08	98.10	166.2	124	141.4	288	102.3	168.2	126.4	143.5	287.5	186	18.1	3"	149	11.9	3"	223	25.4	3"
EAW-FD1552ZK750K5-532AXSP12	102.40	164.9	124.6	141.1	-	104.2													

EAW-FD1553PB370C2-625AXSP08	128.80	205.1	155.9	175.9	-	132.1	206.5	157.8	177.4	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370C2-632AXSP08	124.00	199.8	151.3	171.1	338.1	127.2	201	153.1	172.4	337.3	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370C4-425AXSP06	103.50	175.8	130.5	149.3	-	108.1	178.1	133.3	151.7	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD1553PB370C4-432AXSP08	104.60	171.4	128.3	146	-	106.9	172.4	129.8	147.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370C4-525AXSP08	122.60	197.2	149	168.7	-	125.5	198.6	150.9	170.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370C4-532AXSP08	116.30	188.6	142	161	-	119.1	189.9	143.7	162.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370C4-625AXSP08	128.80	205.1	155.9	175.9	-	132.1	206.5	157.8	177.4	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370C5-425AXSP06	103.50	175.8	130.5	149.3	-	108.1	178.1	133.3	151.7	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD1553PB370C5-432AXSP08	104.60	171.4	128.3	146	-	106.9	172.4	129.8	147.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370C5-525AXSP08	122.60	197.2	149	168.7	-	125.5	198.6	150.9	170.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370C5-532AXSP08	116.30	188.6	142	161	-	119.1	189.9	143.7	162.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370C5-625AXSP08	128.80	205.1	155.9	175.9	-	132.1	206.5	157.8	177.4	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370C5-632AXSP08	124.00	199.8	151.3	171.1	338.1	127.2	201	153.1	172.4	337.3	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370C8-425AXSP06	103.50	175.8	130.5	149.3	-	108.1	178.1	133.3	151.7	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD1553PB370C8-432AXSP08	104.60	171.4	128.3	146	-	106.9	172.4	129.8	147.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370C8-525AXSP08	122.60	197.2	149	168.7	-	125.5	198.6	150.9	170.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370C8-532AXSP08	116.30	188.6	142	161	-	119.1	189.9	143.7	162.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370C8-625AXSP08	128.80	205.1	155.9	175.9	-	132.1	206.5	157.8	177.4	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370C8-632AXSP08	124.00	199.8	151.3	171.1	338.1	127.2	201	153.1	172.4	337.3	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370K2-425AXSP08	109.80	178.7	134.1	152.3	-	112.1	179.7	135.5	153.5	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370K2-432AXSP08	101.90	167.1	125.1	142.3	-	104.2	168	126.3	143.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370K2-525AXSP08	121.10	194.5	147	166.4	-	123.7	195.6	148.4	167.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370K2-532AXSP08	114.20	184.8	139.3	157.8	-	116.5	185.9	140.5	158.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370K2-625AXSP08	128.60	204.4	155.4	175.3	-	131.3	205.5	157.1	176.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370K2-632AXSP08	122.50	197.4	149.3	169.1	334	125.4	198.3	150.9	169.9	332.6	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370K4-425AXSP08	109.80	178.7	134.1	152.3	-	112.1	179.7	135.5	153.5	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370K4-432AXSP08	101.90	167.1	125.1	142.3	-	104.2	168	126.3	143.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370K4-525AXSP08	121.10	194.5	147	166.4	-	123.7	195.6	148.4	167.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370K4-532AXSP08	114.20	184.8	139.3	157.8	-	116.5	185.9	140.5	158.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370K4-625AXSP08	128.60	204.4	155.4	175.3	-	131.3	205.5	157.1	176.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370K4-632AXSP08	122.50	197.4	149.3	169.1	334	125.4	198.3	150.9	169.9	332.6	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370K5-425AXSP08	109.80	178.7	134.1	152.3	-	112.1	179.7	135.5	153.5	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370K5-432AXSP08	101.90	167.1	125.1	142.3	-	104.2	168	126.3	143.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB370K5-525AXSP08	121.10	194.5	147	166.4	-	123.7	195.6	148.4	167.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370K5-532AXSP08	114.20	184.8	139.3	157.8	-	116.5	185.9	140.5	158.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB370K5-625AXSP08	128.60	204.4	155.4	175.3	-	131.3	205.5	157.1	176.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB370K5-632AXSP08	122.50	197.4	149.3	169.1	334	125.4	198.3	150.9	169.9	332.6	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400B3-425AXSP06	-	-	-	-	-	-	-	-	-	-	225	18.9	3"	180	12.4	3"	270	22.8	4"
EAW-FD1553PB400B3-432AXSP08	101.20	165.7	124.1	141.2	-	103.5	166.7	125.5	142.3	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400B3-525AXSP06	-	-	-	-	-	-	-	-	-	-	225	18.9	3"	180	12.4	3"	270	22.8	4"
EAW-FD1553PB400B3-532AXSP08	112.10	181.3	136.6	155	-	114.7	182.7	138.2	156.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	270	16.8	4"	216	13.5	3"	325	23.6	4"
EAW-FD1553PB400B3-632AXSP06	-	-	-	-	-	-	-	-	-	-	270	16.8	4"	216	13.5	3"	325	23.6	4"
EAW-FD1553PB400C3-425AXSP06	103.50	175.8	130.5	149.3	-	108.1	178.1	133.3	151.7	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD1553PB400C3-432AXSP08	104.60	171.4	128.3	146	-	106.9	172.4	129.8	147.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400C3-525AXSP08	122.60	197.2	149	168.7	-	125.5	198.6	150.9	170.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400C3-532AXSP08	116.30	188.6	142	161	-	119.1	189.9	143.7	162.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400C3-625AXSP08	128.80	205.1	155.9	175.9	-	132.1	206.5	157.8	177.4	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400C3-632AXSP08	124.00	199.8	151.3	171.1	338.1	127.2	201	153.1	172.4	337.3	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400C9-425AXSP06	103.50	175.8	130.5	149.3	-	108.1	178.1	133.3	151.7	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD1553PB400C9-432AXSP08	104.60	171.4	128.3	146	-	106.9	172.4	129.8	147.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400C9-525AXSP08	122.60	197.2	149	168.7	-	125.5	198.6	150.9	170.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400C9-532AXSP08	116.30	188.6	142	161	-	119.1	189.9	143.7	162.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400C9-625AXSP08	128.80	205.1	155.9	175.9	-	132.1	206.5	157.8	177.4	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400C9-632AXSP08	124.00	199.8	151.3	171.1	338.1	127.2	201	153.1	172.4	337.3	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400K3-425AXSP08	109.80	178.7	134.1	152.3	-	112.1	179.7	135.5	153.5	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400K3-432AXSP08	101.90	167.1	125.1	142.3	-	104.2	168	126.3	143.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400K3-525AXSP08	121.10	194.5	147	166.4	-	123.7	195.6	148.4	167.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400K3-532AXSP08	114.20	184.8	139.3	157.8	-	116.5	185.9	140.5	158.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400K3-625AXSP08	128.60	204.4	155.4	175.3	-	131.3	205.5	157.1	176.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400K3-632AXSP08	122.50	197.4	149.3	169.1	334	125.4	198.3	150.9	169.9	332.6	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD1553PB400K9-425AXSP08	109.80	178.7	134.1	152.3	-	112.1	179.7	135.5	153.5	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400K9-432AXSP08	101.90	167.1	125.1	142.3	-	104.2	168	126.3	143.2	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD1553PB400K9-525AXSP08	121.10	194.5	147	166.4	-	123.7	195.6	148.4	167.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400K9-532AXSP08	114.20	184.8	139.3	157.8	-	116.5	185.9	140.5	158.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD1553PB400K9-625AXSP08	128.60	204.4	155.4	175.3	-	131.3	205.5	157.1	176.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"</

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3PB550C4-632AXSP08	-	-	-	-	-	141	223.4	169.7	191.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550C5-425AXSP06	115.10	194.4	144.2	165.2	-	119.9	197.4	147.2	167.8	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550C5-432AXSP06	106.00	181.5	134	153.8	-	110.7	184	136.8	156.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550C5-525AXSP08	135.80	219.3	165.4	187.3	-	139	221.2	167.5	189.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550C5-532AXSP08	128.10	208.5	156.6	178.1	-	131.2	210	158.6	179.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550C5-632AXSP08	-	-	-	-	-	141	223.4	169.7	191.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550C8-425AXSP06	115.10	194.4	144.2	165.2	-	119.9	197.4	147.2	167.8	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550C8-432AXSP06	106.00	181.5	134	153.8	-	110.7	184	136.8	156.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550C8-525AXSP08	135.80	219.3	165.4	187.3	-	139	221.2	167.5	189.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550C8-532AXSP08	128.10	208.5	156.6	178.1	-	131.2	210	158.6	179.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550C8-632AXSP08	-	-	-	-	-	141	223.4	169.7	191.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550C9-425AXSP06	115.10	194.4	144.2	165.2	-	119.9	197.4	147.2	167.8	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550C9-432AXSP06	106.00	181.5	134	153.8	-	110.7	184	136.8	156.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550C9-525AXSP08	135.80	219.3	165.4	187.3	-	139	221.2	167.5	189.2	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550C9-532AXSP08	128.10	208.5	156.6	178.1	-	131.2	210	158.6	179.4	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550C9-625AXSP06	-	-	-	-	-	-	-	-	-	-	270	16.8	4"	216	13.5	3"	325	23.6	4"
EAW-FD15S3PB550C9-632AXSP08	-	-	-	-	-	141	223.4	169.7	191.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K2-425AXSP06	110.60	187.3	138.7	158.9	-	115	189.6	141.5	161.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550K2-432AXSP08	110.40	181.3	135.6	154.5	-	113	182.5	137.2	155.6	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD15S3PB550K2-525AXSP08	131.50	211.9	160	181.1	-	134.5	213.1	161.7	182.5	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K2-532AXSP08	123.70	201.1	151.2	171.6	-	126.5	202.4	152.9	172.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K2-625AXSP08	139.80	222.9	169.2	191.2	-	142.9	224.2	171.1	192.3	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K2-632AXSP08	133.40	214.7	162.1	183.6	-	136.5	215.9	163.9	184.8	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K3-425AXSP06	110.60	187.3	138.7	158.9	-	115	189.6	141.5	161.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550K3-432AXSP08	110.40	181.3	135.6	154.5	-	113	182.5	137.2	155.6	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD15S3PB550K3-525AXSP08	131.50	211.9	160	181.1	-	134.5	213.1	161.7	182.5	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K3-532AXSP08	123.70	201.1	151.2	171.6	-	126.5	202.4	152.9	172.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K3-625AXSP08	139.80	222.9	169.2	191.2	-	142.9	224.2	171.1	192.3	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K3-632AXSP08	133.40	214.7	162.1	183.6	-	136.5	215.9	163.9	184.8	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K4-425AXSP06	110.60	187.3	138.7	158.9	-	115	189.6	141.5	161.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550K4-432AXSP08	110.40	181.3	135.6	154.5	-	113	182.5	137.2	155.6	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD15S3PB550K4-525AXSP08	131.50	211.9	160	181.1	-	134.5	213.1	161.7	182.5	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K4-532AXSP08	123.70	201.1	151.2	171.6	-	126.5	202.4	152.9	172.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K4-625AXSP08	139.80	222.9	169.2	191.2	-	142.9	224.2	171.1	192.3	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K4-632AXSP08	133.40	214.7	162.1	183.6	-	136.5	215.9	163.9	184.8	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K5-425AXSP06	110.60	187.3	138.7	158.9	-	115	189.6	141.5	161.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550K5-432AXSP08	110.40	181.3	135.6	154.5	-	113	182.5	137.2	155.6	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD15S3PB550K5-525AXSP08	131.50	211.9	160	181.1	-	134.5	213.1	161.7	182.5	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K5-532AXSP08	123.70	201.1	151.2	171.6	-	126.5	202.4	152.9	172.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K5-625AXSP08	139.80	222.9	169.2	191.2	-	142.9	224.2	171.1	192.3	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K5-632AXSP08	133.40	214.7	162.1	183.6	-	136.5	215.9	163.9	184.8	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K8-425AXSP06	110.60	187.3	138.7	158.9	-	115	189.6	141.5	161.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550K8-432AXSP08	110.40	181.3	135.6	154.5	-	113	182.5	137.2	155.6	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD15S3PB550K8-525AXSP08	131.50	211.9	160	181.1	-	134.5	213.1	161.7	182.5	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K8-532AXSP08	123.70	201.1	151.2	171.6	-	126.5	202.4	152.9	172.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K8-625AXSP08	139.80	222.9	169.2	191.2	-	142.9	224.2	171.1	192.3	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K8-632AXSP08	133.40	214.7	162.1	183.6	-	136.5	215.9	163.9	184.8	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K9-425AXSP06	110.60	187.3	138.7	158.9	-	115	189.6	141.5	161.2	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550K9-432AXSP08	110.40	181.3	135.6	154.5	-	113	182.5	137.2	155.6	-	135	21.5	3"	108	17.9	2"	162	30.1	3"
EAW-FD15S3PB550K9-525AXSP08	131.50	211.9	160	181.1	-	134.5	213.1	161.7	182.5	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K9-532AXSP08	123.70	201.1	151.2	171.6	-	126.5	202.4	152.9	172.8	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550K9-625AXSP08	139.80	222.9	169.2	191.2	-	142.9	224.2	171.1	192.3	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550K9-632AXSP08	133.40	214.7	162.1	183.6	-	136.5	215.9	163.9	184.8	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550R3-425AXSP06	112.70	190.6	141.3	161.7	-	117.3	193.1	144.1	164.1	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550R3-432AXSP06	103.70	177.6	131.2	150.5	-	108.1	179.9	134	152.8	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB550R3-525AXSP08	133.80	215.4	162.6	184.4	-	136.6	216.8	164.6	185.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550R3-532AXSP08	125.80	204.4	153.8	174.7	-	128.7	206	155.5	176.1	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB550R3-625AXSP08	142.10	226.6	172.1	194.2	-	145.3	228	173.9	195.7	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB550R3-632AXSP08	135.60	218.2	164.8	186.8	-	138.6	219.8	166.8	188.1	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB750K2-425AXSP06	116.50	196.6	145.7	167	-	121.2	199.7	149	169.7	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB750K2-432AXSP06	107.30	183.6	135.4	155.5	-	111.8	186	138.3	158	-	180	17.5	3"	144	11.5	3"	216	24.6	3"
EAW-FD15S3PB750K2-525AXSP06	173.50	221.9	167.5	189.8	-	140.7	223.7	169.6	191.6	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB750K2-532AXSP08	129.60	210.8	158.4	180	-	132.6	212.4	160.3	181.7	-	169	22.2	3"	135	14.7	3"	203	31.2	3"
EAW-FD15S3PB750K2-625AXSP08	146.20	233.1	176.9	199.9	-	149.5	234.9	178.9	201.5	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB750K2-632AXSP08	139.50	224.8	169.6	192.3	-	142.7	226.4	171.9	193.6	-	203	23.2	3"	162	15.3	3"	244	32.6	3"
EAW-FD15S3PB750K3-425AXSP06	116.50	196.6	145.7	167	-	121.2	199.7												

EAW-FD1553ZB370C2-425AXSP08	122.10	198.3	149.2	169.2	-	124.6	199.5	150.5	170.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370C2-432AXSP08	113.50	185.9	139.1	158.2	-	115.8	186.7	140.5	159.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370C2-525AXSP08	132.40	212.5	160.8	181.8	-	135.1	213.9	162.5	183.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370C2-532AXSP08	124.90	202.6	152.6	173	-	127.7	203.6	154.1	174.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370C2-625AXSP08	140.40	223.6	170	191.8	374.9	143.9	224.9	171.9	193.2	373.7	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370C2-632AXSP08	134.60	217	164.1	185.6	367.1	137.8	218.2	166	187	365.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370C4-425AXSP08	122.10	198.3	149.2	169.2	-	124.6	199.5	150.5	170.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370C4-432AXSP08	113.50	185.9	139.1	158.2	-	115.8	186.7	140.5	159.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370C4-525AXSP08	132.40	212.5	160.8	181.8	-	135.1	213.9	162.5	183.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370C4-532AXSP08	124.90	202.6	152.6	173	-	127.7	203.6	154.1	174.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370C4-625AXSP08	140.40	223.6	170	191.8	374.9	143.9	224.9	171.9	193.2	373.7	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370C5-625AXSP08	140.40	223.6	170	191.8	374.9	143.9	224.9	171.9	193.2	373.7	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370C5-632AXSP08	134.60	217	164.1	185.6	367.1	137.8	218.2	166	187	365.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370C8-425AXSP08	122.10	198.3	149.2	169.2	-	124.6	199.5	150.5	170.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370C8-432AXSP08	113.50	185.9	139.1	158.2	-	115.8	186.7	140.5	159.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370C8-525AXSP08	132.40	212.5	160.8	181.8	-	135.1	213.9	162.5	183.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370C8-532AXSP08	124.90	202.6	152.6	173	-	127.7	203.6	154.1	174.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370C8-625AXSP08	140.40	223.6	170	191.8	374.9	143.9	224.9	171.9	193.2	373.7	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370C8-632AXSP08	134.60	217	164.1	185.6	367.1	137.8	218.2	166	187	365.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K2-425AXSP08	118.70	192.7	145	164.6	-	121	193.5	146.3	165.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K2-432AXSP08	110.10	180.1	134.9	153.5	-	112.4	180.8	136.2	154.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K2-525AXSP08	129.30	207.7	157	177.7	-	131.9	208.5	158.5	178.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K2-532AXSP08	121.70	197	148.3	168.4	-	124.2	198	149.8	169.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K2-625AXSP08	138.30	220.4	167.6	189.1	368.9	141.3	221	169	189.9	367	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K2-632AXSP08	131.50	212.1	160.6	181.8	358.6	134.7	213	162	182.6	356.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K4-425AXSP08	118.70	192.7	145	164.6	-	121	193.5	146.3	165.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K4-432AXSP08	110.10	180.1	134.9	153.5	-	112.4	180.8	136.2	154.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K4-525AXSP08	129.30	207.7	157	177.7	-	131.9	208.5	158.5	178.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K4-532AXSP08	121.70	197	148.3	168.4	-	124.2	198	149.8	169.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K4-625AXSP08	138.30	220.4	167.6	189.1	368.9	141.3	221	169	189.9	367	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K4-632AXSP08	131.50	212.1	160.6	181.8	358.6	134.7	213	162	182.6	356.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K5-425AXSP08	118.70	192.7	145	164.6	-	121	193.5	146.3	165.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K5-432AXSP08	110.10	180.1	134.9	153.5	-	112.4	180.8	136.2	154.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K5-525AXSP08	129.30	207.7	157	177.7	-	131.9	208.5	158.5	178.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K5-532AXSP08	121.70	197	148.3	168.4	-	124.2	198	149.8	169.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K5-625AXSP08	138.30	220.4	167.6	189.1	368.9	141.3	221	169	189.9	367	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K5-632AXSP08	131.50	212.1	160.6	181.8	358.6	134.7	213	162	182.6	356.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K8-425AXSP08	118.70	192.7	145	164.6	-	121	193.5	146.3	165.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K8-432AXSP08	110.10	180.1	134.9	153.5	-	112.4	180.8	136.2	154.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB370K8-525AXSP08	129.30	207.7	157	177.7	-	131.9	208.5	158.5	178.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K8-532AXSP08	121.70	197	148.3	168.4	-	124.2	198	149.8	169.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB370K8-625AXSP08	138.30	220.4	167.6	189.1	368.9	141.3	221	169	189.9	367	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB370K8-632AXSP08	131.50	212.1	160.6	181.8	358.6	134.7	213	162	182.6	356.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB400B3-425AXSP08	117.90	191.6	143.9	163.3	-	120.5	192.5	145.5	164.7	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400B3-432AXSP08	110.00	179.7	134.7	153.3	-	112.3	180.7	136.2	154.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400B3-525AXSP08	127.10	204	154.3	174.6	-	130.1	205.4	156.1	176.1	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400B3-532AXSP08	120.30	195.1	147	166.8	-	123.2	196.3	148.8	168.1	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400B3-625AXSP06	-	-	-	-	-	-	-	-	-	-	304	17.3	4"	244	14.5	3"	365	24.4	4"
EAW-FD1553ZB400B3-632AXSP08	129.20	208.4	157.9	178.4	352	132.4	209.7	159.5	179.8	350.6	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB400C3-425AXSP08	122.10	198.3	149.2	169.2	-	124.6	199.5	150.5	170.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400C3-432AXSP08	113.50	185.9	139.1	158.2	-	115.8	186.7	140.5	159.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400C3-525AXSP08	132.40	212.5	160.8	181.8	-	135.1	213.9	162.5	183.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400C3-532AXSP08	124.90	202.6	152.6	173	-	127.7	203.6	154.1	174.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400C3-625AXSP08	140.40	223.6	170	191.8	374.9	143.9	224.9	171.9	193.2	373.7	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB400C3-632AXSP08	134.60	217	164.1	185.6	367.1	137.8	218.2	166	187	365.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB400C9-425AXSP08	122.10	198.3	149.2	169.2	-	124.6	199.5	150.5	170.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400C9-432AXSP08	113.50	185.9	139.1	158.2	-	115.8	186.7	140.5	159.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400C9-525AXSP08	132.40	212.5	160.8	181.8	-	135.1	213.9	162.5	183.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400C9-532AXSP08	124.90	202.6	152.6	173	-	127.7	203.6	154.1	174.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400C9-625AXSP08	140.40	223.6	170	191.8	374.9	143.9	224.9	171.9	193.2	373.7	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB400C9-632AXSP08	134.60	217	164.1	185.6	367.1	137.8	218.2	166	187	365.5	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB400K3-425AXSP08	118.70	192.7	145	164.6	-	121	193.5	146.3	165.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400K3-432AXSP08	110.10	180.1	134.9	153.5	-	112.4	180.8	136.2	154.3	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB400K3-525AXSP08	129.30	207.7	157	177.7	-	131.9	208.5	158.5	178.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400K3-532AXSP08	121.70	197	148.3	168.4	-	124.2	198	149.8	169.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB400K3-625AXSP08	138.30																		

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3ZB550C3-632AXSP08	150.10	241.5	182.4	206.4	-	153.4	242.9	184.3	207.9	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C4-425AXSP06	125.20	211.8	156.9	179.8	-	130.3	214.5	160.1	182.5	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550C4-432AXSP08	124.80	205	153.3	174.5	-	127.6	206.3	155	175.8	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550C4-525AXSP08	146.80	236.8	178.5	202.6	-	150	238.4	180.8	203.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C4-532AXSP08	137.90	224.6	168.6	191.5	-	141	225.8	170.6	192.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C4-625AXSP08	156.90	250.2	189.8	214.4	-	160.7	252.1	192.2	216.3	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C4-632AXSP08	150.10	241.5	182.4	206.4	-	153.4	242.9	184.3	207.9	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C5-425AXSP06	125.20	211.8	156.9	179.8	-	130.3	214.5	160.1	182.5	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550C5-432AXSP08	124.80	205	153.3	174.5	-	127.6	206.3	155	175.8	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550C5-525AXSP08	146.80	236.8	178.5	202.6	-	150	238.4	180.8	203.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C5-532AXSP08	137.90	224.6	168.6	191.5	-	141	225.8	170.6	192.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C5-625AXSP08	156.90	250.2	189.8	214.4	-	160.7	252.1	192.2	216.3	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C5-632AXSP08	150.10	241.5	182.4	206.4	-	153.4	242.9	184.3	207.9	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C8-425AXSP06	125.20	211.8	156.9	179.8	-	130.3	214.5	160.1	182.5	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550C8-432AXSP08	124.80	205	153.3	174.5	-	127.6	206.3	155	175.8	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550C8-525AXSP08	146.80	236.8	178.5	202.6	-	150	238.4	180.8	203.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C8-532AXSP08	137.90	224.6	168.6	191.5	-	141	225.8	170.6	192.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C8-625AXSP08	156.90	250.2	189.8	214.4	-	160.7	252.1	192.2	216.3	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C8-632AXSP08	150.10	241.5	182.4	206.4	-	153.4	242.9	184.3	207.9	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C9-425AXSP06	125.20	211.8	156.9	179.8	-	130.3	214.5	160.1	182.5	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550C9-432AXSP08	124.80	205	153.3	174.5	-	127.6	206.3	155	175.8	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550C9-525AXSP08	146.80	236.8	178.5	202.6	-	150	238.4	180.8	203.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C9-532AXSP08	137.90	224.6	168.6	191.5	-	141	225.8	170.6	192.9	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550C9-625AXSP08	156.90	250.2	189.8	214.4	-	160.7	252.1	192.2	216.3	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550C9-632AXSP08	150.10	241.5	182.4	206.4	-	153.4	242.9	184.3	207.9	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K2-425AXSP06	119.60	203	150.4	172.3	-	124.6	205.2	153.3	174.7	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550K2-432AXSP08	119.80	196.6	147.1	167.5	-	122.3	197.5	148.5	168.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550K2-525AXSP08	141.20	227.4	171.5	194.5	-	144.1	228.3	173.3	195.6	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K2-532AXSP08	132.50	215.2	161.8	183.8	-	135.3	216.4	163.5	184.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K2-625AXSP06	151.50	241.1	183.1	206.8	-	154.7	242.2	185	208.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K2-632AXSP08	144.10	232.1	175.3	198.5	-	147.4	233.2	177.2	199.8	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K3-425AXSP06	119.60	203	150.4	172.3	-	124.6	205.2	153.3	174.7	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550K3-432AXSP08	119.80	196.6	147.1	167.5	-	122.3	197.5	148.5	168.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550K3-525AXSP08	141.20	227.4	171.5	194.5	-	144.1	228.3	173.3	195.6	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K3-532AXSP08	132.50	215.2	161.8	183.8	-	135.3	216.4	163.5	184.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K3-625AXSP06	151.50	241.1	183.1	206.8	-	154.7	242.2	185	208.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K3-632AXSP08	144.10	232.1	175.3	198.5	-	147.4	233.2	177.2	199.8	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K4-425AXSP06	119.60	203	150.4	172.3	-	124.6	205.2	153.3	174.7	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550K4-432AXSP08	119.80	196.6	147.1	167.5	-	122.3	197.5	148.5	168.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550K4-525AXSP08	141.20	227.4	171.5	194.5	-	144.1	228.3	173.3	195.6	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K4-532AXSP08	132.50	215.2	161.8	183.8	-	135.3	216.4	163.5	184.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K4-625AXSP06	151.50	241.1	183.1	206.8	-	154.7	242.2	185	208.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K4-632AXSP08	144.10	232.1	175.3	198.5	-	147.4	233.2	177.2	199.8	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K5-425AXSP06	119.60	203	150.4	172.3	-	124.6	205.2	153.3	174.7	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550K5-432AXSP08	119.80	196.6	147.1	167.5	-	122.3	197.5	148.5	168.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550K5-525AXSP08	141.20	227.4	171.5	194.5	-	144.1	228.3	173.3	195.6	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K5-532AXSP08	132.50	215.2	161.8	183.8	-	135.3	216.4	163.5	184.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K5-625AXSP06	151.50	241.1	183.1	206.8	-	154.7	242.2	185	208.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K5-632AXSP08	144.10	232.1	175.3	198.5	-	147.4	233.2	177.2	199.8	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K8-425AXSP06	119.60	203	150.4	172.3	-	124.6	205.2	153.3	174.7	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550K8-432AXSP08	119.80	196.6	147.1	167.5	-	122.3	197.5	148.5	168.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550K8-525AXSP08	141.20	227.4	171.5	194.5	-	144.1	228.3	173.3	195.6	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K8-532AXSP08	132.50	215.2	161.8	183.8	-	135.3	216.4	163.5	184.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K8-625AXSP06	151.50	241.1	183.1	206.8	-	154.7	242.2	185	208.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K8-632AXSP08	144.10	232.1	175.3	198.5	-	147.4	233.2	177.2	199.8	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K9-425AXSP06	119.60	203	150.4	172.3	-	124.6	205.2	153.3	174.7	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550K9-432AXSP08	119.80	196.6	147.1	167.5	-	122.3	197.5	148.5	168.5	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550K9-525AXSP08	141.20	227.4	171.5	194.5	-	144.1	228.3	173.3	195.6	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K9-532AXSP08	132.50	215.2	161.8	183.8	-	135.3	216.4	163.5	184.7	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550K9-625AXSP06	151.50	241.1	183.1	206.8	-	154.7	242.2	185	208.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550K9-632AXSP08	144.10	232.1	175.3	198.5	-	147.4	233.2	177.2	199.8	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD15S3ZB550R3-425AXSP06	122.10	206.9	153.3	175.5	-	127	209.3	156.4	178	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD15S3ZB550R3-432AXSP08	122.00	200.2	149.8	170.6	-	124.7	201.6	151.5	171.7	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD15S3ZB550R3-525AXSP08	143.70	231.8	174.9	198.1	-	146.8	232.9	176.8	199.3	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550R3-532AXSP08	134.80	219.3	164.7	187.1	-	137.7	220.6	166.6	188.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD15S3ZB550R3-625AXSP08	154.00	245.7	186.5	210.7	-	157.4	247	188.5	211.8	-	225	24							

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZB750K9-625AXSP08	159.00	253.7	192.3	217.3	-	162.7	255	194.6	219.1	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB750K9-632AXSP08	151.70	244	184.5	208.7	-	155.1	245.8	186.4	210.3	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB750R3-425AXSP06	124.10	209.8	155.7	178.3	-	129.2	212.8	158.8	180.8	-	203	18.2	3"	162	12	3"	244	25.6	3"
EAW-FD1553ZB750R3-432AXSP08	124.10	203.6	152.1	173.4	-	126.7	204.8	154	174.7	-	152	21.9	3"	122	14.4	3"	183	30.7	3"
EAW-FD1553ZB750R3-525AXSP08	145.50	234.8	177.1	200.6	-	148.9	236.3	179.1	202.2	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB750R3-532AXSP08	136.70	222.5	167	189.8	-	139.8	223.6	169	191.1	-	186	22.7	3"	149	15	3"	223	31.9	3"
EAW-FD1553ZB750R3-625AXSP08	155.80	248.2	188.3	212.8	-	159.3	249.8	190.5	214.4	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZB750R3-632AXSP08	148.40	239.2	180.7	204.8	-	151.9	240.5	182.8	206.2	-	225	24	3"	180	15.8	3"	270	29.9	4"
EAW-FD1553ZK370C2-425AXSP06	124.80	207.3	154.8	176.8	-	128.8	208.9	157	178.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370C2-432AXSP08	123.70	200.4	150.8	171.1	-	125.7	201	151.7	171.6	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370C2-525AXSP08	145.20	230.9	175.1	197.8	-	147.5	231.5	176.3	198.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C2-532AXSP08	136.60	219.4	165.7	187.7	-	138.9	220.1	167	188.3	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C2-625AXSP08	155.10	243.8	186	209.4	-	157.7	244.4	187.4	210.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C2-632AXSP08	148.60	235.8	179.3	202.3	-	151	236.2	180.3	202.9	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C4-425AXSP06	124.80	207.3	154.8	176.8	-	128.8	208.9	157	178.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370C4-432AXSP08	123.70	200.4	150.8	171.1	-	125.7	201	151.7	171.6	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370C4-525AXSP08	145.20	230.9	175.1	197.8	-	147.5	231.5	176.3	198.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C4-532AXSP08	136.60	219.4	165.7	187.7	-	138.9	220.1	167	188.3	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C4-625AXSP08	155.10	243.8	186	209.4	-	157.7	244.4	187.4	210.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C4-632AXSP08	148.60	235.8	179.3	202.3	-	151	236.2	180.3	202.9	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C5-425AXSP06	124.80	207.3	154.8	176.8	-	128.8	208.9	157	178.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370C5-432AXSP08	123.70	200.4	150.8	171.1	-	125.7	201	151.7	171.6	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370C5-525AXSP08	145.20	230.9	175.1	197.8	-	147.5	231.5	176.3	198.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C5-532AXSP08	136.60	219.4	165.7	187.7	-	138.9	220.1	167	188.3	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C5-625AXSP08	155.10	243.8	186	209.4	-	157.7	244.4	187.4	210.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C5-632AXSP08	148.60	235.8	179.3	202.3	-	151	236.2	180.3	202.9	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C8-425AXSP06	124.80	207.3	154.8	176.8	-	128.8	208.9	157	178.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370C8-432AXSP08	123.70	200.4	150.8	171.1	-	125.7	201	151.7	171.6	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370C8-525AXSP08	145.20	230.9	175.1	197.8	-	147.5	231.5	176.3	198.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C8-532AXSP08	136.60	219.4	165.7	187.7	-	138.9	220.1	167	188.3	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370C8-625AXSP08	155.10	243.8	186	209.4	-	157.7	244.4	187.4	210.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370C8-632AXSP08	148.60	235.8	179.3	202.3	-	151	236.2	180.3	202.9	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K2-425AXSP06	120.50	200.7	150	171	-	124.4	202	152	172.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370K2-432AXSP08	119.70	193.8	145.8	165.5	-	121.6	194.1	146.6	165.8	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370K2-525AXSP08	141.00	223.9	170	191.9	-	143	224.4	171.1	192.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K2-532AXSP08	132.60	212.4	160.7	181.9	-	134.5	212.7	161.6	182.4	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K2-625AXSP08	151.30	237.7	181.8	204.5	-	153.7	237.9	182.6	204.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K2-632AXSP08	144.20	229.2	174.3	196.5	-	146.6	229.2	175.2	196.8	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K4-425AXSP06	120.50	200.7	150	171	-	124.4	202	152	172.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370K4-432AXSP08	119.70	193.8	145.8	165.5	-	121.6	194.1	146.6	165.8	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370K4-525AXSP08	141.00	223.9	170	191.9	-	143	224.4	171.1	192.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K4-532AXSP08	132.60	212.4	160.7	181.9	-	134.5	212.7	161.6	182.4	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K4-625AXSP08	151.30	237.7	181.8	204.5	-	153.7	237.9	182.6	204.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K4-632AXSP08	144.20	229.2	174.3	196.5	-	146.6	229.2	175.2	196.8	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K5-425AXSP06	120.50	200.7	150	171	-	124.4	202	152	172.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370K5-432AXSP08	119.70	193.8	145.8	165.5	-	121.6	194.1	146.6	165.8	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370K5-525AXSP08	141.00	223.9	170	191.9	-	143	224.4	171.1	192.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K5-532AXSP08	132.60	212.4	160.7	181.9	-	134.5	212.7	161.6	182.4	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K5-625AXSP08	151.30	237.7	181.8	204.5	-	153.7	237.9	182.6	204.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K5-632AXSP08	144.20	229.2	174.3	196.5	-	146.6	229.2	175.2	196.8	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K8-425AXSP06	120.50	200.7	150	171	-	124.4	202	152	172.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK370K8-432AXSP08	119.70	193.8	145.8	165.5	-	121.6	194.1	146.6	165.8	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK370K8-525AXSP08	141.00	223.9	170	191.9	-	143	224.4	171.1	192.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K8-532AXSP08	132.60	212.4	160.7	181.9	-	134.5	212.7	161.6	182.4	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK370K8-625AXSP08	151.30	237.7	181.8	204.5	-	153.7	237.9	182.6	204.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK370K8-632AXSP08	144.20	229.2	174.3	196.5	-	146.6	229.2	175.2	196.8	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK400B3-425AXSP06	120.50	200.5	149.8	170.8	-	124.5	202.1	152.2	172.6	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK400B3-432AXSP08	120.10	194.5	146.3	166.1	-	122	195	147.3	166.6	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK400B3-525AXSP08	139.80	223.3	168.6	190.6	-	142.1	222.7	170.1	191.2	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK400B3-532AXSP08	132.10	212	160.4	181.5	-	134.5	212.6	161.3	182	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK400B3-625AXSP08	148.60	233.5	178.4	200.7	-	151.4	234.2	179.8	201.6	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK400B3-632AXSP08	142.90	227	172.6	194.6	-	145.4	227.6	173.8	195.4	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK400C3-425AXSP06	124.80	207.3	154.8	176.8	-	128.8	208.9	157	178.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK400C3-432AXSP08	123.70	200.4	150.8	171.1	-	125.7	201	151.7	171.6	-	152	23.8	3"	122	15.8	3"	183	33.5	3"
EAW-FD1553ZK400C3-525AXSP08	145.20	230.9	175.1	197.8	-	147.5	231.5	176.3	198.6	-	186	24.7	3"	149	16.3	3"	223	34.7	3"

EAW-FD1553ZK550C2-532AXSP08	151.30	243.7	183.8	208.6	-	153.9	244.4	185.1	209.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550C2-625AXSP08	173.00	273.2	208.3	234.8	-	176.1	274.3	209.8	236	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C2-632AXSP08	165.00	263.2	199.3	225.2	-	167.9	263.7	200.8	226.3	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C3-425AXSP06	138.90	230.6	171.8	196.1	-	143.1	232.5	174.4	198	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C3-432AXSP06	127.80	214.3	159.2	182	-	132	216.2	161.6	184	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C3-525AXSP06	153.00	252.7	189.3	215.6	-	158.2	254.7	192.4	217.6	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK550C3-532AXSP08	151.30	243.7	183.8	208.6	-	153.9	244.4	185.1	209.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550C3-625AXSP08	173.00	273.2	208.3	234.8	-	176.1	274.3	209.8	236	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C3-632AXSP08	165.00	263.2	199.3	225.2	-	167.9	263.7	200.8	226.3	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C4-425AXSP06	138.90	230.6	171.8	196.1	-	143.1	232.5	174.4	198	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C4-432AXSP06	127.80	214.3	159.2	182	-	132	216.2	161.6	184	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C4-525AXSP06	153.00	252.7	189.3	215.6	-	158.2	254.7	192.4	217.6	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK550C4-532AXSP08	151.30	243.7	183.8	208.6	-	153.9	244.4	185.1	209.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550C4-625AXSP08	173.00	273.2	208.3	234.8	-	176.1	274.3	209.8	236	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C4-632AXSP08	165.00	263.2	199.3	225.2	-	167.9	263.7	200.8	226.3	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C5-425AXSP06	138.90	230.6	171.8	196.1	-	143.1	232.5	174.4	198	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C5-432AXSP06	127.80	214.3	159.2	182	-	132	216.2	161.6	184	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C5-525AXSP06	153.00	252.7	189.3	215.6	-	158.2	254.7	192.4	217.6	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK550C5-532AXSP08	151.30	243.7	183.8	208.6	-	153.9	244.4	185.1	209.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550C5-625AXSP08	173.00	273.2	208.3	234.8	-	176.1	274.3	209.8	236	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C5-632AXSP08	165.00	263.2	199.3	225.2	-	167.9	263.7	200.8	226.3	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C8-425AXSP06	138.90	230.6	171.8	196.1	-	143.1	232.5	174.4	198	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C8-432AXSP06	127.80	214.3	159.2	182	-	132	216.2	161.6	184	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C8-525AXSP06	153.00	252.7	189.3	215.6	-	158.2	254.7	192.4	217.6	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK550C8-532AXSP08	151.30	243.7	183.8	208.6	-	153.9	244.4	185.1	209.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550C8-625AXSP08	173.00	273.2	208.3	234.8	-	176.1	274.3	209.8	236	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C8-632AXSP08	165.00	263.2	199.3	225.2	-	167.9	263.7	200.8	226.3	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C9-425AXSP06	138.90	230.6	171.8	196.1	-	143.1	232.5	174.4	198	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C9-432AXSP06	127.80	214.3	159.2	182	-	132	216.2	161.6	184	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550C9-525AXSP06	153.00	252.7	189.3	215.6	-	158.2	254.7	192.4	217.6	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK550C9-532AXSP08	151.30	243.7	183.8	208.6	-	153.9	244.4	185.1	209.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550C9-625AXSP08	173.00	273.2	208.3	234.8	-	176.1	274.3	209.8	236	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550C9-632AXSP08	165.00	263.2	199.3	225.2	-	167.9	263.7	200.8	226.3	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K2-425AXSP06	132.90	220.5	164.4	187.7	-	136.9	222.1	166.9	189.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K2-432AXSP06	122.20	205.2	152.6	174.3	-	126.2	206.7	154.7	176.1	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K2-525AXSP08	154.30	246.1	186.8	210.8	-	156.9	246.8	188	211.7	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K2-532AXSP08	144.90	233	175.8	199.3	-	147.3	233.5	177.3	200	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K2-625AXSP08	166.20	261.8	199.6	224.9	-	168.6	262.2	200.9	225.4	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K2-632AXSP08	158.10	251.4	190.7	215.4	-	160.5	251.9	192.2	216.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K3-425AXSP06	132.90	220.5	164.4	187.7	-	136.9	222.1	166.9	189.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K3-432AXSP06	122.20	205.2	152.6	174.3	-	126.2	206.7	154.7	176.1	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K3-525AXSP08	154.30	246.1	186.8	210.8	-	156.9	246.8	188	211.7	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K3-532AXSP08	144.90	233	175.8	199.3	-	147.3	233.5	177.3	200	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K3-625AXSP08	166.20	261.8	199.6	224.9	-	168.6	262.2	200.9	225.4	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K3-632AXSP08	158.10	251.4	190.7	215.4	-	160.5	251.9	192.2	216.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K4-425AXSP06	132.90	220.5	164.4	187.7	-	136.9	222.1	166.9	189.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K4-432AXSP06	122.20	205.2	152.6	174.3	-	126.2	206.7	154.7	176.1	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K4-525AXSP08	154.30	246.1	186.8	210.8	-	156.9	246.8	188	211.7	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K4-532AXSP08	144.90	233	175.8	199.3	-	147.3	233.5	177.3	200	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K4-625AXSP08	166.20	261.8	199.6	224.9	-	168.6	262.2	200.9	225.4	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K4-632AXSP08	158.10	251.4	190.7	215.4	-	160.5	251.9	192.2	216.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K5-425AXSP06	132.90	220.5	164.4	187.7	-	136.9	222.1	166.9	189.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K5-432AXSP06	122.20	205.2	152.6	174.3	-	126.2	206.7	154.7	176.1	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K5-525AXSP08	154.30	246.1	186.8	210.8	-	156.9	246.8	188	211.7	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K5-532AXSP08	144.90	233	175.8	199.3	-	147.3	233.5	177.3	200	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K5-625AXSP08	166.20	261.8	199.6	224.9	-	168.6	262.2	200.9	225.4	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K5-632AXSP08	158.10	251.4	190.7	215.4	-	160.5	251.9	192.2	216.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K8-425AXSP06	132.90	220.5	164.4	187.7	-	136.9	222.1	166.9	189.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K8-432AXSP06	122.20	205.2	152.6	174.3	-	126.2	206.7	154.7	176.1	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K8-525AXSP08	154.30	246.1	186.8	210.8	-	156.9	246.8	188	211.7	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K8-532AXSP08	144.90	233	175.8	199.3	-	147.3	233.5	177.3	200	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK550K8-625AXSP08	166.20	261.8	199.6	224.9	-	168.6	262.2	200.9	225.4	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K8-632AXSP08	158.10	251.4	190.7	215.4	-	160.5	251.9	192.2	216.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK550K9-425AXSP06	132.90	220.5	164.4	187.7	-	136.9	222.1	166.9	189.4	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K9-432AXSP06	122.20	205.2	152.6	174.3	-	126.2	206.7	154.7	176.1	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK550K9-525AXSP08	154.30	246.1	186.8	210.8	-	156.9	246.8	188	211.7	-	186	24.7							

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1553ZK750K4-625AXSP08	175.10	276.8	210.9	237.7	-	178.3	277.9	212.5	238.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K4-632AXSP08	166.90	266	201.6	227.9	-	169.9	267	203.2	229.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K5-425AXSP06	140.70	233.7	174.1	198.7	-	144.9	235.9	177	201.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750K5-432AXSP06	130.00	217.7	161.7	184.9	-	134.2	219.8	164.3	186.9	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750K5-525AXSP06	155.00	255.5	191.5	218.2	-	160	258	194.7	220.4	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK750K5-532AXSP08	153.20	247	186.1	210.9	-	155.7	248	187.7	212.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK750K5-625AXSP08	175.10	276.8	210.9	237.7	-	178.3	277.9	212.5	238.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K5-632AXSP08	166.90	266	201.6	227.9	-	169.9	267	203.2	229.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K8-425AXSP06	140.70	233.7	174.1	198.7	-	144.9	235.9	177	201.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750K8-432AXSP06	130.00	217.7	161.7	184.9	-	134.2	219.8	164.3	186.9	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750K8-525AXSP06	155.00	255.5	191.5	218.2	-	160	258	194.7	220.4	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK750K8-532AXSP08	153.20	247	186.1	210.9	-	155.7	248	187.7	212.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK750K8-625AXSP08	175.10	276.8	210.9	237.7	-	178.3	277.9	212.5	238.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K8-632AXSP08	166.90	266	201.6	227.9	-	169.9	267	203.2	229.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K9-425AXSP06	140.70	233.7	174.1	198.7	-	144.9	235.9	177	201.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750K9-432AXSP06	130.00	217.7	161.7	184.9	-	134.2	219.8	164.3	186.9	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750K9-525AXSP06	155.00	255.5	191.5	218.2	-	160	258	194.7	220.4	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK750K9-532AXSP08	153.20	247	186.1	210.9	-	155.7	248	187.7	212.1	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK750K9-625AXSP08	175.10	276.8	210.9	237.7	-	178.3	277.9	212.5	238.7	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750K9-632AXSP08	166.90	266	201.6	227.9	-	169.9	267	203.2	229.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750R3-425AXSP06	137.90	229	170.5	194.7	-	142.1	231.1	173.2	196.8	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750R3-432AXSP06	127.30	213.4	158.6	181.2	-	131.4	215.5	161	183.2	-	203	19.7	3"	162	13	3"	244	27.7	3"
EAW-FD1553ZK750R3-525AXSP06	151.50	250.2	187.8	213.4	-	156.6	252.5	190.5	215.8	-	254	21.5	3"	203	14.1	3"	304	25.4	4"
EAW-FD1553ZK750R3-532AXSP08	150.10	241.6	182.3	206.8	-	152.8	242.5	183.8	207.5	-	186	24.7	3"	149	16.3	3"	223	34.7	3"
EAW-FD1553ZK750R3-625AXSP08	171.60	270.8	206.2	232.4	-	174.5	271.7	208	233.5	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1553ZK750R3-632AXSP08	163.50	260.6	197.7	223.4	-	166.3	261.4	199.2	224.1	-	225	26	3"	180	17.1	3"	270	32.7	4"
EAW-FD1554PB370C2-425AXSP04	129.50	228.7	167.8	193.7	403.5	137.5	232.7	172.6	197.6	404.1	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB370C2-432AXSP06	138.90	227.6	170.5	194	-	142	229	172.3	195.4	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370C2-525AXSP06	162.90	262.2	197.9	224.2	-	166.7	264.1	200.6	226.1	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C2-532AXSP06	154.50	250.6	188.6	214.3	-	158.2	252.4	190.9	215.8	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C2-625AXSP06	171.20	272.7	207.3	233.9	-	175.6	274.6	210.1	236.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C2-632AXSP06	164.80	265.5	201	227.4	449.6	169	267.6	203.5	229.2	448.5	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C4-425AXSP04	129.50	228.7	167.8	193.7	403.5	137.5	232.7	172.6	197.6	404.1	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB370C4-432AXSP06	138.90	227.6	170.5	194	-	142	229	172.3	195.4	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370C4-525AXSP06	162.90	262.2	197.9	224.2	-	166.7	264.1	200.6	226.1	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C4-532AXSP06	154.50	250.6	188.6	214.3	-	158.2	252.4	190.9	215.8	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C4-625AXSP06	171.20	272.7	207.3	233.9	-	175.6	274.6	210.1	236.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C4-632AXSP06	164.80	265.5	201	227.4	449.6	169	267.6	203.5	229.2	448.5	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C5-425AXSP04	129.50	228.7	167.8	193.7	403.5	137.5	232.7	172.6	197.6	404.1	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB370C5-432AXSP06	138.90	227.6	170.5	194	-	142	229	172.3	195.4	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370C5-525AXSP06	162.90	262.2	197.9	224.2	-	166.7	264.1	200.6	226.1	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C5-532AXSP06	154.50	250.6	188.6	214.3	-	158.2	252.4	190.9	215.8	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C5-625AXSP06	171.20	272.7	207.3	233.9	-	175.6	274.6	210.1	236.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C5-632AXSP06	164.80	265.5	201	227.4	449.6	169	267.6	203.5	229.2	448.5	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C8-425AXSP04	129.50	228.7	167.8	193.7	403.5	137.5	232.7	172.6	197.6	404.1	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB370C8-432AXSP06	138.90	227.6	170.5	194	-	142	229	172.3	195.4	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370C8-525AXSP06	162.90	262.2	197.9	224.2	-	166.7	264.1	200.6	226.1	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C8-532AXSP06	154.50	250.6	188.6	214.3	-	158.2	252.4	190.9	215.8	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370C8-625AXSP06	171.20	272.7	207.3	233.9	-	175.6	274.6	210.1	236.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370C8-632AXSP06	164.80	265.5	201	227.4	449.6	169	267.6	203.5	229.2	448.5	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370K2-425AXSP06	145.80	237.3	178.3	202.4	-	149	238.7	180	203.9	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370K2-432AXSP06	135.40	221.8	166	189	-	138.3	223.1	167.9	190.2	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370K2-525AXSP06	160.80	258.6	195.3	221.2	-	164.3	260	197.6	222.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370K2-532AXSP06	151.60	245.9	185	210.1	-	154.8	247	187	211.4	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370K2-625AXSP06	170.90	271.8	206.9	233.4	-	174.5	273.3	208.8	234.7	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370K2-632AXSP06	162.70	262.4	198.7	224.8	444.1	166.7	263.7	200.5	226.2	442.2	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370K4-425AXSP06	145.80	237.3	178.3	202.4	-	149	238.7	180	203.9	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370K4-432AXSP06	135.40	221.8	166	189	-	138.3	223.1	167.9	190.2	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370K4-525AXSP06	160.80	258.6	195.3	221.2	-	164.3	260	197.6	222.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370K4-532AXSP06	151.60	245.9	185	210.1	-	154.8	247	187	211.4	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB370K4-625AXSP06	170.90	271.8	206.9	233.4	-	174.5	273.3	208.8	234.7	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370K4-632AXSP06	162.70	262.4	198.7	224.8	444.1	166.7	263.7	200.5	226.2	442.2	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB370K5-425AXSP06	145.80	237.3	178.3	202.4	-	149	238.7	180	203.9	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370K5-432AXSP06	135.40	221.8	166	189	-	138.3	223.1	167.9	190.2	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB370K5-525AXSP06	160.80	258.6	195.3	221.2	-	164.3	260	197.6	222.7	-	225	23.4							

EAW-FD1554PB400K9-532AXSP06	151.60	245.9	185	210.1	-	154.8	247	187	211.4	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB400K9-625AXSP06	170.90	271.8	206.9	233.4	-	174.5	273.3	208.8	234.7	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB400K9-632AXSP06	162.70	262.4	198.7	224.8	444.1	166.7	263.7	200.5	226.2	442.2	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB400R3-425AXSP06	147.40	239.8	180.2	204.8	-	150.5	241.3	182.2	206.1	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB400R3-432AXSP06	136.90	224.4	167.8	191.1	-	139.8	225.6	169.6	192.5	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB400R3-525AXSP06	162.40	261.2	197.3	223.4	-	166	262.4	199.3	224.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB400R3-532AXSP06	153.10	248.4	187	212.1	-	156.6	249.6	188.9	213.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB400R3-625AXSP06	172.40	274.3	208.7	235.6	-	176.1	275.9	210.8	236.9	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB400R3-632AXSP06	164.20	265	200.3	227	448.6	168.3	266.4	202.5	228.1	446.9	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550B3-425AXSP04	134.10	236.1	173.5	200	416.8	142.3	240.5	178.7	204.2	418.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550B3-432AXSP06	143.50	235.8	176.4	200.9	-	147	237.7	178.6	202.7	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB550B3-525AXSP04	-	-	-	-	-	-	-	-	-	-	338	15.8	4"	270	10.4	4"	406	22.2	4"
EAW-FD1554PB550B3-532AXSP06	-	-	-	-	-	162.9	260.5	196.7	222.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550B3-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.2	4"	487	19.6	(2) 4"
EAW-FD1554PB550B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.2	4"	487	19.6	(2) 4"
EAW-FD1554PB550C2-425AXSP04	144.50	252.9	186	214.2	448.2	152.7	257.7	191.2	218.4	449.6	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C2-432AXSP04	132.70	235.8	172.6	199.3	420	140.6	240.1	177.6	203.2	421.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C3-525AXSP06	180.70	291.5	219.7	249.3	-	185	294	222.6	251.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C2-532AXSP06	170.30	277	208.2	236.6	-	174.2	279.5	210.7	238.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C2-632AXSP06	-	-	-	-	-	187.3	297	225.5	254.5	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550C3-425AXSP04	144.50	252.9	186	214.2	448.2	152.7	257.7	191.2	218.4	449.6	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C3-432AXSP04	132.70	235.8	172.6	199.3	420	140.6	240.1	177.6	203.2	421.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C3-525AXSP06	180.70	291.5	219.7	249.3	-	185	294	222.6	251.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C3-532AXSP06	170.30	277	208.2	236.6	-	174.2	279.5	210.7	238.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C3-632AXSP06	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.2	4"	487	19.6	(2) 4"
EAW-FD1554PB550C3-632AXSP06	-	-	-	-	-	187.3	297	225.5	254.5	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550C4-425AXSP04	144.50	252.9	186	214.2	448.2	152.7	257.7	191.2	218.4	449.6	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C4-432AXSP04	132.70	235.8	172.6	199.3	420	140.6	240.1	177.6	203.2	421.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C4-525AXSP06	180.70	291.5	219.7	249.3	-	185	294	222.6	251.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C4-532AXSP06	170.30	277	208.2	236.6	-	174.2	279.5	210.7	238.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C4-632AXSP06	-	-	-	-	-	187.3	297	225.5	254.5	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550C5-425AXSP04	144.50	252.9	186	214.2	448.2	152.7	257.7	191.2	218.4	449.6	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C5-432AXSP04	132.70	235.8	172.6	199.3	420	140.6	240.1	177.6	203.2	421.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C5-525AXSP06	180.70	291.5	219.7	249.3	-	185	294	222.6	251.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C5-532AXSP06	170.30	277	208.2	236.6	-	174.2	279.5	210.7	238.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C5-632AXSP06	-	-	-	-	-	187.3	297	225.5	254.5	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550C8-425AXSP04	144.50	252.9	186	214.2	448.2	152.7	257.7	191.2	218.4	449.6	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C8-432AXSP04	132.70	235.8	172.6	199.3	420	140.6	240.1	177.6	203.2	421.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C8-525AXSP06	180.70	291.5	219.7	249.3	-	185	294	222.6	251.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C8-532AXSP06	170.30	277	208.2	236.6	-	174.2	279.5	210.7	238.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C8-632AXSP06	-	-	-	-	-	187.3	297	225.5	254.5	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550C9-425AXSP04	144.50	252.9	186	214.2	448.2	152.7	257.7	191.2	218.4	449.6	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C9-432AXSP04	132.70	235.8	172.6	199.3	420	140.6	240.1	177.6	203.2	421.4	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550C9-525AXSP06	180.70	291.5	219.7	249.3	-	185	294	222.6	251.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C9-532AXSP06	170.30	277	208.2	236.6	-	174.2	279.5	210.7	238.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550C9-625AXSP04	-	-	-	-	-	-	-	-	-	-	406	17	4"	325	11.2	4"	487	19.6	(2) 4"
EAW-FD1554PB550C9-632AXSP06	-	-	-	-	-	187.3	297	225.5	254.5	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K2-432AXSP06	138.70	243.4	179	206.1	430.6	146.6	247.6	183.7	209.8	430.9	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550K2-525AXSP06	146.70	241	180.2	205.1	-	150.1	242.6	182.3	206.7	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB550K2-532AXSP06	174.70	281.6	212.6	240.7	-	178.7	283.3	214.8	242.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550K2-532AXSP06	164.50	267.1	200.7	228	-	168	268.9	203.1	229.9	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550K2-625AXSP06	185.80	296.4	224.9	254.1	-	189.9	298.1	227.5	256	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K2-632AXSP06	177.20	285.4	215.4	244	-	181.4	286.9	218.2	246.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K3-425AXSP04	138.70	243.4	179	206.1	430.6	146.6	247.6	183.7	209.8	430.9	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550K3-432AXSP06	146.70	241	180.2	205.1	-	150.1	242.6	182.3	206.7	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB550K3-525AXSP06	174.70	281.6	212.6	240.7	-	178.7	283.3	214.8	242.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550K3-525AXSP06	164.50	267.1	200.7	228	-	168	268.9	203.1	229.9	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550K3-625AXSP06	185.80	296.4	224.9	254.1	-	189.9	298.1	227.5	256	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K3-625AXSP06	177.20	285.4	215.4	244	-	181.4	286.9	218.2	246.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K3-632AXSP06	177.20	285.4	215.4	244	-	181.4	286.9	218.2	246.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K4-425AXSP04	138.70	243.4	179	206.1	430.6	146.6	247.6	183.7	209.8	430.9	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB550K4-432AXSP06	146.70	241	180.2	205.1	-	150.1	242.6	182.3	206.7	-	180	22	3"	144	14.5	3"	216	30.9	3"
EAW-FD1554PB550K4-525AXSP06	174.70	281.6	212.6	240.7	-	178.7	283.3	214.8	242.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550K4-532AXSP06	164.50	267.1	200.7	228	-	168	268.9	203.1	229.9	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB550K4-625AXSP06	185.80	296.4	224.9	254.1	-	189.9	298.1	227.5	256	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB550K4-632AXSP06	177.20	285.4	215.4	244	-	181.4	286.9	218.2	246.1	-	270	21.3	4"	216	16.5	3"	325	29.9	4"

EAW-FD1554PB750K4-425AXSP04	146.20	255.7	188.1	216.4	-	154.6	260.6	193.3	220.9	-	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K4-432AXSP04	134.20	238.5	174.4	201.4	424.7	142.2	242.6	179.5	205.5	426.2	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K4-525AXSP06	182.70	295.4	222.6	252.2	-	187.2	297.3	225.4	254.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K4-532AXSP06	172.20	280	210.4	239.1	-	176.2	282.2	213.3	241.3	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K4-625AXSP06	194.30	309.9	235.1	265.8	-	198.7	312.3	237.8	267.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K4-632AXSP06	185.30	298.8	225.4	255.5	-	189.6	300.9	228.4	257.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K5-425AXSP04	146.20	255.7	188.1	216.4	-	154.6	260.6	193.3	220.9	-	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K5-432AXSP04	134.20	238.5	174.4	201.4	424.7	142.2	242.6	179.5	205.5	426.2	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K5-525AXSP06	182.70	295.4	222.6	252.2	-	187.2	297.3	225.4	254.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K5-532AXSP06	172.20	280	210.4	239.1	-	176.2	282.2	213.3	241.3	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K5-625AXSP06	194.30	309.9	235.1	265.8	-	198.7	312.3	237.8	267.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K5-632AXSP06	185.30	298.8	225.4	255.5	-	189.6	300.9	228.4	257.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K8-425AXSP04	146.20	257.7	188.1	216.4	-	154.6	260.6	193.3	220.9	-	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K8-432AXSP04	134.20	238.5	174.4	201.4	424.7	142.2	242.6	179.5	205.5	426.2	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K8-525AXSP06	182.70	295.4	222.6	252.2	-	187.2	297.3	225.4	254.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K8-532AXSP06	172.20	280	210.4	239.1	-	176.2	282.2	213.3	241.3	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K8-625AXSP06	194.30	309.9	235.1	265.8	-	198.7	312.3	237.8	267.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K8-632AXSP06	185.30	298.8	225.4	255.5	-	189.6	300.9	228.4	257.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K9-425AXSP04	146.20	255.7	188.1	216.4	-	154.6	260.6	193.3	220.9	-	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K9-432AXSP04	134.20	238.5	174.4	201.4	424.7	142.2	242.6	179.5	205.5	426.2	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750K9-525AXSP06	182.70	295.4	222.6	252.2	-	187.2	297.3	225.4	254.7	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K9-532AXSP06	172.20	280	210.4	239.1	-	176.2	282.2	213.3	241.3	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750K9-625AXSP06	194.30	309.9	235.1	265.8	-	198.7	312.3	237.8	267.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750K9-632AXSP06	185.30	298.8	225.4	255.5	-	189.6	300.9	228.4	257.8	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750R3-425AXSP04	143.10	250.9	184.4	212.3	443.8	151.4	255.3	189.5	216.4	445.2	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750R3-432AXSP04	131.40	233.8	171	197.6	417	139.6	238	175.9	201.5	417.5	270	14.8	4"	216	12.1	3"	325	20.8	4"
EAW-FD1554PB750R3-525AXSP06	179.20	289.4	218.2	247.2	-	183.6	291.6	220.8	249.5	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750R3-532AXSP06	168.90	275	206.4	234.5	-	172.9	276.9	209.2	236.6	-	225	23.4	3"	180	15.4	3"	270	29.1	4"
EAW-FD1554PB750R3-625AXSP06	190.30	303.6	230.5	260.5	-	194.8	305.9	233.1	262.4	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554PB750R3-632AXSP06	181.90	292.9	221.2	250.7	-	186.1	294.9	224	252.7	-	270	21.3	4"	216	16.5	3"	325	29.9	4"
EAW-FD1554ZB730C2-425AXSP06	162.10	263.5	198.1	225.2	-	165.6	265.1	200.3	226.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C2-432AXSP06	150.60	246.8	184.8	210.3	-	153.9	248	186.7	211.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C2-525AXSP06	178.10	286	216.2	244.7	-	182.1	287.8	218.9	246.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C2-532AXSP06	168.40	272.9	205.4	233.2	-	171.9	274.2	207.7	234.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C2-625AXSP06	187.80	299.3	227.6	256.8	501.1	192.5	301.1	230.2	258.7	499.5	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C2-632AXSP06	180.20	290.2	220	248.7	491.5	184.3	291.8	222.1	250.5	489.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C4-425AXSP06	162.10	263.5	198.1	225.2	-	165.6	265.1	200.3	226.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C4-432AXSP06	150.60	246.8	184.8	210.3	-	153.9	248	186.7	211.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C4-525AXSP06	178.10	286	216.2	244.7	-	182.1	287.8	218.9	246.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C4-532AXSP06	168.40	272.9	205.4	233.2	-	171.9	274.2	207.7	234.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C4-625AXSP06	187.80	299.3	227.6	256.8	501.1	192.5	301.1	230.2	258.7	499.5	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C4-632AXSP06	180.20	290.2	220	248.7	491.5	184.3	291.8	222.1	250.5	489.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C5-425AXSP06	162.10	263.5	198.1	225.2	-	165.6	265.1	200.3	226.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C5-432AXSP06	150.60	246.8	184.8	210.3	-	153.9	248	186.7	211.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C5-525AXSP06	178.10	286	216.2	244.7	-	182.1	287.8	218.9	246.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C5-532AXSP06	168.40	272.9	205.4	233.2	-	171.9	274.2	207.7	234.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C5-625AXSP06	187.80	299.3	227.6	256.8	501.1	192.5	301.1	230.2	258.7	499.5	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C5-632AXSP06	180.20	290.2	220	248.7	491.5	184.3	291.8	222.1	250.5	489.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C8-425AXSP06	162.10	263.5	198.1	225.2	-	165.6	265.1	200.3	226.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C8-432AXSP06	150.60	246.8	184.8	210.3	-	153.9	248	186.7	211.5	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730C8-525AXSP06	178.10	286	216.2	244.7	-	182.1	287.8	218.9	246.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C8-532AXSP06	168.40	272.9	205.4	233.2	-	171.9	274.2	207.7	234.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730C8-625AXSP06	187.80	299.3	227.6	256.8	501.1	192.5	301.1	230.2	258.7	499.5	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730C8-632AXSP06	180.20	290.2	220	248.7	491.5	184.3	291.8	222.1	250.5	489.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730K2-425AXSP06	157.60	256.1	192.5	218.6	-	160.7	257.2	194.3	219.9	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730K2-432AXSP06	146.30	239.3	179.3	203.9	-	149.2	240.1	180.9	205	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730K2-525AXSP06	174.30	279.5	211.5	239.3	-	177.7	280.4	213.5	240.5	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730K2-532AXSP06	163.80	265.3	200	226.9	-	167.2	266.6	201.9	228	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730K2-625AXSP06	185.00	294.6	224.2	252.9	493.7	189	295.8	226.3	254.2	490.5	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730K2-632AXSP06	176.00	284.1	215.1	243.2	480	180.2	284.9	217	244.3	477.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB730K4-425AXSP06	157.60	256.1	192.5	218.6	-	160.7	257.2	194.3	219.9	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730K4-432AXSP06	146.30	239.3	179.3	203.9	-	149.2	240.1	180.9	205	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB730K4-525AXSP06	174.30	279.5	211.5	239.3	-	177.7	280.4	213.5	240.5	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB730K4-532AXSP06	163.80	265.3	200	226.9	-	167.2	266.6	201.9	228	-	254	24.4	3"	203	16.				

EAW-FD1554ZB400K3-632AXSP06	176.00	284.1	215.1	243.2	480	180.2	284.9	217	244.3	477.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB400K9-425AXSP06	157.60	256.1	192.5	218.6	-	160.7	257.2	194.3	219.9	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB400K9-432AXSP06	146.30	239.3	179.3	203.9	-	149.2	240.1	180.9	205	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB400K9-525AXSP06	174.30	279.5	211.5	239.3	-	177.7	280.4	213.5	240.5	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB400K9-532AXSP06	163.80	265.3	200	226.9	-	167.2	266.6	201.9	228	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB400K9-625AXSP06	185.00	294.6	224.2	252.9	493.7	189	295.8	226.3	254.2	490.5	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB400K9-632AXSP06	176.00	284.1	215.1	243.2	480	180.2	284.9	217	244.3	477.2	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB400R3-425AXSP06	159.40	259.2	194.8	221.2	-	162.6	260.5	196.7	222.7	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB400R3-432AXSP06	148.00	242.4	181.5	206.4	-	151.1	243.4	183.3	207.7	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB400R3-525AXSP06	176.10	282.6	213.7	241.9	-	179.6	283.7	215.9	243.2	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB400R3-532AXSP06	165.60	268.4	202.2	229.5	-	169.4	269.8	204.2	230.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB400R3-625AXSP06	186.90	297.8	226.6	255.5	498.5	191	298.8	228.5	256.7	496.1	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB400R3-632AXSP06	178.10	287.1	217.3	246.1	485.4	182.1	288.1	219.3	247.3	487.6	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550R3-425AXSP04	146.30	258.2	189.5	218.7	455.8	155.2	262.8	195	222.9	456.4	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550R3-432AXSP06	156.80	257.1	192.5	219	-	160.3	258.6	194.6	220.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550R3-525AXSP06	183.90	296	223.4	253	-	188.1	298.1	226.3	255.2	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550R3-532AXSP06	174.50	282.8	212.8	241.8	-	178.6	285	215.5	243.7	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550R3-625AXSP04	-	-	-	-	-	-	-	-	-	-	456	14.3	(2) 4"	365	11.9	4"	548	20.1	(2) 4"
EAW-FD1554ZB550R3-632AXSP06	-	-	-	-	-	190.8	302.1	229.6	258.7	506.3	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C2-425AXSP04	157.00	275.2	202.8	233.2	487.2	165.9	280.1	207.8	237.5	487.6	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550C2-432AXSP06	165.80	272.5	203.7	231.9	-	169.3	273.9	205.9	233.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550C2-525AXSP06	197.70	318.8	240.6	272.9	-	202.3	320.8	243.6	274.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C2-532AXSP06	186.10	302.7	227.4	258.3	-	190.1	304.2	230.1	260	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C2-625AXSP06	209.90	335	254.2	287.2	-	214.9	337	257.1	289.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C2-632AXSP06	200.50	323	244.1	276.5	-	205.2	325.3	246.9	278.5	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C3-425AXSP04	157.00	275.2	202.8	233.2	487.2	165.9	280.1	207.8	237.5	487.6	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550C3-432AXSP06	165.80	272.5	203.7	231.9	-	169.3	273.9	205.9	233.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550C3-525AXSP06	197.70	318.8	240.6	272.9	-	202.3	320.8	243.6	274.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C3-532AXSP06	186.10	302.7	227.4	258.3	-	190.1	304.2	230.1	260	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C3-625AXSP06	209.90	335	254.2	287.2	-	214.9	337	257.1	289.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C3-632AXSP06	200.50	323	244.1	276.5	-	205.2	325.3	246.9	278.5	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C4-425AXSP04	157.00	275.2	202.8	233.2	487.2	165.9	280.1	207.8	237.5	487.6	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550C4-432AXSP06	165.80	272.5	203.7	231.9	-	169.3	273.9	205.9	233.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550C4-525AXSP06	197.70	318.8	240.6	272.9	-	202.3	320.8	243.6	274.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C4-532AXSP06	186.10	302.7	227.4	258.3	-	190.1	304.2	230.1	260	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C4-625AXSP06	209.90	335	254.2	287.2	-	214.9	337	257.1	289.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C4-632AXSP06	200.50	323	244.1	276.5	-	205.2	325.3	246.9	278.5	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C5-425AXSP04	157.00	275.2	202.8	233.2	487.2	165.9	280.1	207.8	237.5	487.6	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550C5-432AXSP06	165.80	272.5	203.7	231.9	-	169.3	273.9	205.9	233.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550C5-525AXSP06	197.70	318.8	240.6	272.9	-	202.3	320.8	243.6	274.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C5-532AXSP06	186.10	302.7	227.4	258.3	-	190.1	304.2	230.1	260	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C5-625AXSP06	209.90	335	254.2	287.2	-	214.9	337	257.1	289.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C5-632AXSP06	200.50	323	244.1	276.5	-	205.2	325.3	246.9	278.5	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C8-425AXSP04	157.00	275.2	202.8	233.2	487.2	165.9	280.1	207.8	237.5	487.6	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550C8-432AXSP06	165.80	272.5	203.7	231.9	-	169.3	273.9	205.9	233.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550C8-525AXSP06	197.70	318.8	240.6	272.9	-	202.3	320.8	243.6	274.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C8-532AXSP06	186.10	302.7	227.4	258.3	-	190.1	304.2	230.1	260	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C8-625AXSP06	209.90	335	254.2	287.2	-	214.9	337	257.1	289.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C8-632AXSP06	200.50	323	244.1	276.5	-	205.2	325.3	246.9	278.5	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C9-425AXSP04	157.00	275.2	202.8	233.2	487.2	165.9	280.1	207.8	237.5	487.6	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550C9-432AXSP06	165.80	272.5	203.7	231.9	-	169.3	273.9	205.9	233.6	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550C9-525AXSP06	197.70	318.8	240.6	272.9	-	202.3	320.8	243.6	274.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C9-532AXSP06	186.10	302.7	227.4	258.3	-	190.1	304.2	230.1	260	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550C9-625AXSP06	209.90	335	254.2	287.2	-	214.9	337	257.1	289.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550C9-632AXSP06	200.50	323	244.1	276.5	-	205.2	325.3	246.9	278.5	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550K2-425AXSP04	149.70	264	193.8	223.4	465.7	158.5	268.1	198.9	227.5	466.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550K2-432AXSP06	159.20	261.1	195.3	222.5	-	162.5	262.9	197.4	223.9	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550K2-525AXSP06	190.00	306.1	231.1	261.9	-	194.2	307.8	233.4	263.3	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550K2-532AXSP06	178.50	289.9	217.9	247.8	-	182.3	291.4	220.5	249	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550K2-625AXSP06	202.70	322.8	244.9	276.5	-	206.9	324.3	247.7	278.2	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550K2-632AXSP06	192.80	310.4	235	266	-	197.2	311.9	237.1	267.3	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB550K3-425AXSP04	149.70	264	193.8	223.4	465.7	158.5	268.1	198.9	227.5	466.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB550K3-432AXSP06	159.20	261.1	195.3	222.5	-	162.5	262.9	197.4	223.9	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB550K3-525AXSP06	190.00	306.1	231.1	261.9	-	194.2	307.8	233.4	263.3	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB550K3-532AXSP06	17																		

EAW-FD1554ZB750K2-625AXSP06	212.70	339.2	257.6	290.7	-	217.6	341.4	260.3	293	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K2-632AXSP06	203.00	326.8	246.8	279.7	-	207.6	328.8	249.8	281.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K3-425AXSP04	159.00	278.5	204.9	235.8	493.2	168	283.4	210.4	240.2	493.7	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K3-432AXSP04	145.60	259.5	189.5	219.2	462.1	154.4	263.8	195	223.5	462.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K3-525AXSP06	199.90	322.7	243.4	276.2	-	204.6	324.9	246.6	278	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K3-532AXSP06	188.00	306.2	229.9	261.2	-	192.3	307.8	232.7	263	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K3-625AXSP06	212.70	339.2	257.6	290.7	-	217.6	341.4	260.3	293	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K3-632AXSP06	203.00	326.8	246.8	279.7	-	207.6	328.8	249.8	281.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K4-425AXSP04	159.00	278.5	204.9	235.8	493.2	168	283.4	210.4	240.2	493.7	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K4-432AXSP04	145.60	259.5	189.5	219.2	462.1	154.4	263.8	195	223.5	462.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K4-525AXSP06	199.90	322.7	243.4	276.2	-	204.6	324.9	246.6	278	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K4-532AXSP06	188.00	306.2	229.9	261.2	-	192.3	307.8	232.7	263	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K4-625AXSP06	212.70	339.2	257.6	290.7	-	217.6	341.4	260.3	293	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K4-632AXSP06	203.00	326.8	246.8	279.7	-	207.6	328.8	249.8	281.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K5-425AXSP04	159.00	278.5	204.9	235.8	493.2	168	283.4	210.4	240.2	493.7	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K5-432AXSP04	145.60	259.5	189.5	219.2	462.1	154.4	263.8	195	223.5	462.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K5-525AXSP06	199.90	322.7	243.4	276.2	-	204.6	324.9	246.6	278	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K5-532AXSP06	188.00	306.2	229.9	261.2	-	192.3	307.8	232.7	263	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K5-625AXSP06	212.70	339.2	257.6	290.7	-	217.6	341.4	260.3	293	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K5-632AXSP06	203.00	326.8	246.8	279.7	-	207.6	328.8	249.8	281.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K8-425AXSP04	159.00	278.5	204.9	235.8	493.2	168	283.4	210.4	240.2	493.7	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K8-432AXSP04	145.60	259.5	189.5	219.2	462.1	154.4	263.8	195	223.5	462.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K8-525AXSP06	199.90	322.7	243.4	276.2	-	204.6	324.9	246.6	278	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K8-532AXSP06	188.00	306.2	229.9	261.2	-	192.3	307.8	232.7	263	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K8-625AXSP06	212.70	339.2	257.6	290.7	-	217.6	341.4	260.3	293	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K8-632AXSP06	203.00	326.8	246.8	279.7	-	207.6	328.8	249.8	281.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K9-425AXSP04	159.00	278.5	204.9	235.8	493.2	168	283.4	210.4	240.2	493.7	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K9-432AXSP04	145.60	259.5	189.5	219.2	462.1	154.4	263.8	195	223.5	462.2	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750K9-525AXSP06	199.90	322.7	243.4	276.2	-	204.6	324.9	246.6	278	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K9-532AXSP06	188.00	306.2	229.9	261.2	-	192.3	307.8	232.7	263	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750K9-625AXSP06	212.70	339.2	257.6	290.7	-	217.6	341.4	260.3	293	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750K9-632AXSP06	203.00	326.8	246.8	279.7	-	207.6	328.8	249.8	281.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750R3-425AXSP04	155.50	273.2	200.8	231.1	483.2	164.4	277.4	206.2	235.5	483.5	304	15.3	4"	244	13.2	3"	365	21.5	4"
EAW-FD1554ZB750R3-432AXSP06	164.60	270.3	202.1	230.4	-	168.4	272.2	204.5	232.2	-	203	22.7	3"	162	15	3"	244	31.9	3"
EAW-FD1554ZB750R3-525AXSP06	195.80	316.1	238.3	270.2	-	200.3	318.1	241.3	272.4	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750R3-532AXSP06	184.40	299.8	225.3	255.9	-	188.6	301.8	228	257.6	-	254	24.4	3"	203	16.1	3"	304	29.6	4"
EAW-FD1554ZB750R3-625AXSP06	208.40	324.2	252.3	284.6	-	213	333.9	254.8	286.7	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZB750R3-632AXSP06	198.60	319.9	241.8	273.9	-	203.3	322.1	244.6	275.8	-	304	21.8	4"	244	17.5	3"	365	30.6	4"
EAW-FD1554ZK370C2-425AXSP04	157.70	270.5	200.6	229.8	472.5	164.8	273.2	204.4	232.7	470.9	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK370C2-432AXSP06	164.30	266.7	200.2	227.5	-	167	267	201.7	228.1	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK370C2-525AXSP06	195.20	310.7	235.9	266.3	-	198.6	311.4	237.3	267.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C2-532AXSP06	184.30	295.5	223.4	252.9	-	187.3	296.4	225.1	253.6	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C2-625AXSP06	207.40	326	249.2	280.4	-	210.9	327.1	250.9	281.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C2-632AXSP06	198.80	315.8	239.9	270.6	-	202.1	316.3	241.6	271.8	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C4-425AXSP04	157.70	270.5	200.6	229.8	472.5	164.8	273.2	204.4	232.7	470.9	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK370C4-432AXSP06	164.30	266.7	200.2	227.5	-	167	267	201.7	228.1	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK370C4-525AXSP06	195.20	310.7	235.9	266.3	-	198.6	311.4	237.3	267.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C4-532AXSP06	184.30	295.5	223.4	252.9	-	187.3	296.4	225.1	253.6	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C4-625AXSP06	207.40	326	249.2	280.4	-	210.9	327.1	250.9	281.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C4-632AXSP06	198.80	315.8	239.9	270.6	-	202.1	316.3	241.6	271.8	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C5-425AXSP04	157.70	270.5	200.6	229.8	472.5	164.8	273.2	204.4	232.7	470.9	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK370C5-432AXSP06	164.30	266.7	200.2	227.5	-	167	267	201.7	228.1	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK370C5-525AXSP06	195.20	310.7	235.9	266.3	-	198.6	311.4	237.3	267.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C5-532AXSP06	184.30	295.5	223.4	252.9	-	187.3	296.4	225.1	253.6	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C5-625AXSP06	207.40	326	249.2	280.4	-	210.9	327.1	250.9	281.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C5-632AXSP06	198.80	315.8	239.9	270.6	-	202.1	316.3	241.6	271.8	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C8-425AXSP04	157.70	270.5	200.6	229.8	472.5	164.8	273.2	204.4	232.7	470.9	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK370C8-432AXSP06	164.30	266.7	200.2	227.5	-	167	267	201.7	228.1	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK370C8-525AXSP06	195.20	310.7	235.9	266.3	-	198.6	311.4	237.3	267.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C8-532AXSP06	184.30	295.5	223.4	252.9	-	187.3	296.4	225.1	253.6	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK370C8-625AXSP06	207.40	326	249.2	280.4	-	210.9	327.1	250.9	281.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370C8-632AXSP06	198.80	315.8	239.9	270.6	-	202.1	316.3	241.6	271.8	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK370K2-425AXSP04	152.20	261.5	193.7	222.4	456.6	159.2	264.2	197.7	224.9	455.3	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK370K2-432AXSP06	159.00	257.4	193.8	220	-	161.4	257.8	194.9	220.6	-	203	24.7							

EAW-FD1554ZK400C9-532AXSP06	184.30	295.5	223.4	252.9	-	187.3	296.4	225.1	253.6	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400C9-625AXSP06	207.40	326	249.2	280.4	-	210.9	327.1	250.9	281.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400C9-632AXSP06	198.80	315.8	239.9	270.6	-	202.1	316.3	241.6	271.8	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400K3-425AXSP04	152.20	261.5	193.7	222.4	456.6	159.2	264.2	197.7	224.9	455.3	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK400K3-432AXSP06	159.00	257.4	193.8	220	-	161.4	257.8	194.9	220.6	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK400K3-525AXSP06	189.60	301.7	228.9	258.3	-	192.6	301.9	230.4	259.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400K3-532AXSP06	178.50	286.5	216.6	245	-	181.3	286.8	217.8	245.7	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400K3-625AXSP06	202.70	318.2	243.1	273.4	-	205.5	318.5	244.5	274	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400K3-632AXSP06	193.00	306.5	233.1	262.8	-	196.1	306.9	234.4	263.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400K9-425AXSP04	152.20	261.5	193.7	222.4	456.6	159.2	264.2	197.7	224.9	455.3	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK400K9-432AXSP06	159.00	257.4	193.8	220	-	161.4	257.8	194.9	220.6	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK400K9-525AXSP06	189.60	301.7	228.9	258.3	-	192.6	301.9	230.4	259.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400K9-532AXSP06	178.50	286.5	216.6	245	-	181.3	286.8	217.8	245.7	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400K9-625AXSP06	202.70	318.2	243.1	273.4	-	205.5	318.5	244.5	274	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400K9-632AXSP06	193.00	306.5	233.1	262.8	-	196.1	306.9	234.4	263.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400R3-425AXSP04	154.50	265.2	196.5	225.1	462.7	161.4	268.2	200.5	228.1	461.6	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK400R3-432AXSP06	161.10	261.2	196.4	223	-	163.6	261.8	197.6	223.6	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK400R3-525AXSP06	191.90	305.5	231.8	261.5	-	195	305.9	233.3	262.6	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400R3-532AXSP06	180.70	289.9	219.4	248.2	-	183.8	290.5	220.8	248.7	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK400R3-625AXSP06	204.90	321.9	245.8	277	-	208.2	322.3	247.3	277.3	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK400R3-632AXSP06	195.20	310.3	235.9	266.4	-	198.5	310.9	237.3	266.9	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550B3-425AXSP04	165.40	282.6	209.6	240.1	495	172.8	286.2	214.1	243.4	494.6	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550B3-432AXSP04	152.40	264.5	195.1	224.2	465.3	159.7	267.7	199.2	227.5	465.1	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550B3-525AXSP06	203.20	323.7	245.3	277.1	-	206.6	324.7	247.4	278.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550B3-625AXSP06	191.90	308.6	233.3	263.8	-	195.6	309.8	235.2	265.2	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550B3-632AXSP06	214.60	337.8	257.9	290.4	-	218.7	339.3	260	291.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550B3-632AXSP06	206.40	328.1	249.3	281.3	-	210.1	329.6	251.4	283	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C2-425AXSP04	176.40	300.6	222.5	255.1	-	183.9	303.8	226.8	258.4	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C2-432AXSP04	161.50	279.2	206	236.6	492.2	168.8	282.3	210.1	239.7	491.5	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C2-525AXSP04	192.80	328.3	244.1	279	568.6	201.5	332.2	249.3	282.9	568.3	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK550C2-532AXSP06	204.00	328.3	247.9	280.7	-	207.7	329.8	249.7	281.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550C2-625AXSP06	231.80	365.8	278.5	314	-	235.8	367.2	281	315.5	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C2-632AXSP06	220.80	352	267.1	301.7	-	224.6	353.1	269	302.7	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C3-425AXSP04	176.40	300.6	222.5	255.1	-	183.9	303.8	226.8	258.4	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C3-432AXSP04	161.50	279.2	206	236.6	492.2	168.8	282.3	210.1	239.7	491.5	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C3-525AXSP04	192.80	328.3	244.1	279	568.6	201.5	332.2	249.3	282.9	568.3	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK550C3-532AXSP06	204.00	328.3	247.9	280.7	-	207.7	329.8	249.7	281.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550C3-625AXSP06	231.80	365.8	278.5	314	-	235.8	367.2	281	315.5	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C3-632AXSP06	220.80	352	267.1	301.7	-	224.6	353.1	269	302.7	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C4-425AXSP04	176.40	300.6	222.5	255.1	-	183.9	303.8	226.8	258.4	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C4-432AXSP04	161.50	279.2	206	236.6	492.2	168.8	282.3	210.1	239.7	491.5	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C4-525AXSP04	192.80	328.3	244.1	279	568.6	201.5	332.2	249.3	282.9	568.3	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK550C4-532AXSP06	204.00	328.3	247.9	280.7	-	207.7	329.8	249.7	281.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550C4-625AXSP06	231.80	365.8	278.5	314	-	235.8	367.2	281	315.5	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C4-632AXSP06	220.80	352	267.1	301.7	-	224.6	353.1	269	302.7	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C5-425AXSP04	176.40	300.6	222.5	255.1	-	183.9	303.8	226.8	258.4	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C5-432AXSP04	161.50	279.2	206	236.6	492.2	168.8	282.3	210.1	239.7	491.5	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C5-525AXSP04	192.80	328.3	244.1	279	568.6	201.5	332.2	249.3	282.9	568.3	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK550C5-532AXSP06	204.00	328.3	247.9	280.7	-	207.7	329.8	249.7	281.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550C5-625AXSP06	231.80	365.8	278.5	314	-	235.8	367.2	281	315.5	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C5-632AXSP06	220.80	352	267.1	301.7	-	224.6	353.1	269	302.7	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C8-425AXSP04	176.40	300.6	222.5	255.1	-	183.9	303.8	226.8	258.4	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C8-432AXSP04	161.50	279.2	206	236.6	492.2	168.8	282.3	210.1	239.7	491.5	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C8-525AXSP04	192.80	328.3	244.1	279	568.6	201.5	332.2	249.3	282.9	568.3	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK550C8-532AXSP06	204.00	328.3	247.9	280.7	-	207.7	329.8	249.7	281.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550C8-625AXSP06	231.80	365.8	278.5	314	-	235.8	367.2	281	315.5	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C8-632AXSP06	220.80	352	267.1	301.7	-	224.6	353.1	269	302.7	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550C9-425AXSP04	176.40	300.6	222.5	255.1	-	183.9	303.8	226.8	258.4	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C9-432AXSP04	161.50	279.2	206	236.6	492.2	168.8	282.3	210.1	239.7	491.5	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550C9-525AXSP04	192.80	328.3	244.1	279	568.6	201.5	332.2	249.3	282.9	568.3	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK550C9-532AXSP06	204.00	328.3	247.9	280.7	-	207.7	329.8	249.7	281.8	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550C9-625AXSP06	231.80	365.8	278.5	314	-	235.8	367.2	281	315.5	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550K3-425AXSP06	168.10	287	212.9	243.9	502.4	175.3	290.8	217.1	247.2	502	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK550K2-432AXSP04	154.10	267.1	197.1	226.6	470.3	161.2	270.5	201.2	229.5	469.4	304								

EAW-FD1554ZK550R3-525AXSP06	212.10	338.2	256.2	289.6	-	215.7	339.2	258.5	290.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550R3-532AXSP06	199.10	320.4	241.7	274.1	-	202.6	321.2	243.4	275.2	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK550R3-625AXSP06	226.50	357.7	272.6	307.1	-	230.4	358.3	274.4	308	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK550R3-632AXSP06	215.60	343.6	260.6	294.3	-	219.4	344.4	262.3	295.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750C4-425AXSP06	204.70	331.6	249.2	283	-	208.3	332.9	251.6	284.6	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK750C4-432AXSP06	189.40	308.5	231.3	263	-	192.8	309.9	233.3	264.3	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK750C4-525AXSP06	225.80	361.1	273.2	309.2	-	230.1	362.8	276.1	311.2	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750C4-532AXSP06	212.30	342.4	257.9	292.9	-	216.3	344.2	260.5	294.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750C4-632AXSP06	229.30	365.7	277	313.2	-	233.4	367.7	279.7	314.9	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750C5-425AXSP06	204.70	331.6	249.2	283	-	208.3	332.9	251.6	284.6	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK750C5-432AXSP06	189.40	308.5	231.3	263	-	192.8	309.9	233.3	264.3	-	203	24.7	3"	162	16.3	3"	244	34.7	3"
EAW-FD1554ZK750C5-525AXSP06	225.80	361.1	273.2	309.2	-	230.1	362.8	276.1	311.2	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750C5-532AXSP06	212.30	342.4	257.9	292.9	-	216.3	344.2	260.5	294.3	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750C5-632AXSP06	229.30	365.7	277	313.2	-	233.4	367.7	279.7	314.9	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K2-425AXSP04	178.70	304.5	225.5	258.5	-	186.4	308.7	230.1	262.3	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K2-432AXSP04	164.30	283.7	209.4	240.4	500.9	171.7	287.3	213.5	243.7	499.8	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K2-525AXSP04	195.10	332.4	247	282.4	576	204.3	336.4	252.3	286.4	575	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750K2-532AXSP06	206.60	332.8	251.1	284.3	-	210.1	334	253.2	285.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750K2-625AXSP06	234.60	370.6	282	317.9	-	238.8	372	284.6	319.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K2-632AXSP06	223.40	356.3	270.2	305.4	-	227.3	357.6	272.3	306.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K3-425AXSP04	178.70	304.5	225.5	258.5	-	186.4	308.7	230.1	262.3	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K3-432AXSP04	164.30	283.7	209.4	240.4	500.9	171.7	287.3	213.5	243.7	499.8	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K3-525AXSP04	195.10	332.4	247	282.4	576	204.3	336.4	252.3	286.4	575	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750K3-532AXSP06	206.60	332.8	251.1	284.3	-	210.1	334	253.2	285.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750K3-625AXSP06	234.60	370.6	282	317.9	-	238.8	372	284.6	319.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K3-632AXSP06	223.40	356.3	270.2	305.4	-	227.3	357.6	272.3	306.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K4-425AXSP04	178.70	304.5	225.5	258.5	-	186.4	308.7	230.1	262.3	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K4-432AXSP04	164.30	283.7	209.4	240.4	500.9	171.7	287.3	213.5	243.7	499.8	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K4-525AXSP04	195.10	332.4	247	282.4	576	204.3	336.4	252.3	286.4	575	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750K4-532AXSP06	206.60	332.8	251.1	284.3	-	210.1	334	253.2	285.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750K4-625AXSP06	234.60	370.6	282	317.9	-	238.8	372	284.6	319.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K4-632AXSP06	223.40	356.3	270.2	305.4	-	227.3	357.6	272.3	306.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K5-425AXSP04	178.70	304.5	225.5	258.5	-	186.4	308.7	230.1	262.3	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K5-432AXSP04	164.30	283.7	209.4	240.4	500.9	171.7	287.3	213.5	243.7	499.8	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K5-525AXSP04	195.10	332.4	247	282.4	576	204.3	336.4	252.3	286.4	575	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750K5-532AXSP06	206.60	332.8	251.1	284.3	-	210.1	334	253.2	285.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750K5-625AXSP06	234.60	370.6	282	317.9	-	238.8	372	284.6	319.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K5-632AXSP06	223.40	356.3	270.2	305.4	-	227.3	357.6	272.3	306.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K8-425AXSP04	178.70	304.5	225.5	258.5	-	186.4	308.7	230.1	262.3	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K8-432AXSP04	164.30	283.7	209.4	240.4	500.9	171.7	287.3	213.5	243.7	499.8	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K8-525AXSP04	195.10	332.4	247	282.4	576	204.3	336.4	252.3	286.4	575	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750K8-532AXSP06	206.60	332.8	251.1	284.3	-	210.1	334	253.2	285.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750K8-625AXSP06	234.60	370.6	282	317.9	-	238.8	372	284.6	319.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K8-632AXSP06	223.40	356.3	270.2	305.4	-	227.3	357.6	272.3	306.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K9-425AXSP04	178.70	304.5	225.5	258.5	-	186.4	308.7	230.1	262.3	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K9-432AXSP04	164.30	283.7	209.4	240.4	500.9	171.7	287.3	213.5	243.7	499.8	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750K9-525AXSP04	195.10	332.4	247	282.4	576	204.3	336.4	252.3	286.4	575	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750K9-532AXSP06	206.60	332.8	251.1	284.3	-	210.1	334	253.2	285.9	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750K9-625AXSP06	234.60	370.6	282	317.9	-	238.8	372	284.6	319.6	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750K9-632AXSP06	223.40	356.3	270.2	305.4	-	227.3	357.6	272.3	306.4	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750R3-425AXSP04	174.90	298.5	220.9	253.1	-	182.5	301.9	225.6	256.8	-	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750R3-432AXSP04	160.70	278	205.2	235.7	490	168.2	281.5	209.5	239	489.9	304	16.6	4"	244	14	3"	365	23.4	4"
EAW-FD1554ZK750R3-525AXSP04	190.80	325	241.8	276.8	563.5	199.6	328.8	246.9	280.6	562.4	378	17.8	4"	302	11.8	4"	453	21.3	(2) 4"
EAW-FD1554ZK750R3-532AXSP06	202.40	326.1	245.9	278.3	-	205.8	327.2	247.8	279.7	-	254	26.4	3"	203	17.4	3"	304	32.4	4"
EAW-FD1554ZK750R3-625AXSP06	229.50	362.1	276.2	311.2	-	233.4	363.3	278.1	312.3	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1554ZK750R3-632AXSP06	218.80	349	264.5	298.8	-	222.8	349.6	266.4	300.2	-	304	23.8	4"	244	18.8	3"	365	33.4	4"
EAW-FD1555PB370C2-425AXSP04	177.60	295.2	220	251	-	183.6	298.5	224	254.3	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD1555PB370C2-432AXSP04	164.60	276.7	205.5	235.1	-	170.4	279.6	209.2	238	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD1555PB370C2-525AXSP04	192.50	319.1	239.3	272.4	547.7	199.6	322.6	243.5	275.9	547.5	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD1555PB370C2-532AXSP04	181.70	305.1	227.6	259.5	527.9	188.7	308.1	231.9	263	527.2	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD1555PB370C2-625AXSP06	222.20	347.5	265.8	298.8	-	225.9	348.8	268.1	300.2	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD1555PB370C2-632AXSP06	214.40	338.4	258	290.6	-	217.8	340	259.7	291.9	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD1555PB370C4-425AXSP04	177.60	295.2	220	251	-	183.6	298.5	224	254.3	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD1555PB370C4-432AXSP04	164.60	276.7	205.5	235.1	-	170.4	279.6	209.2	238	-	270	17.8	4"	216	14.1	3"	325	25	

EAW-FD155SPB370K8-52AXSP04	178.00	299.1	223.3	254.5	516.8	184.6	301.6	226.9	257.2	515.6	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB370K8-62AXSP06	221.80	346.3	265.3	298.2	-	224.9	346.7	266.4	298.4	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB370K8-632AXSP06	212.10	334.4	254.7	287.3	-	215.1	334.9	256.4	287.6	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400B3-42AXSP04	170.80	284.3	212	242.1	-	176.9	287.6	215.9	244.9	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400B3-432AXSP04	158.80	267.6	198.8	227.4	-	164.7	270.3	202.4	230.1	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400B3-52AXSP04	-	-	-	-	-	-	-	-	-	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400B3-532AXSP04	174.60	293.6	219	250	506.8	181.5	297	223.2	253	506.5	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400B3-62AXSP04	-	-	-	-	-	-	-	-	-	-	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB400B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB400C3-42AXSP04	177.60	295.2	220	251	-	183.6	298.5	224	254.3	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400C3-432AXSP04	164.60	276.7	205.5	235.1	-	170.4	279.6	209.2	238	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400C3-52AXSP04	192.50	319.1	239.3	272.4	547.7	199.6	322.6	243.5	275.9	547.5	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400C3-532AXSP04	181.70	305.1	227.6	259.5	527.9	188.7	308.1	231.9	263	527.2	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400C3-62AXSP06	222.20	347.5	265.8	298.8	-	225.9	348.8	268.1	300.2	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400C3-632AXSP06	214.40	338.4	258	290.6	-	217.8	340	259.7	291.9	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400C9-42AXSP04	177.60	295.2	220	251	-	183.6	298.5	224	254.3	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400C9-432AXSP04	164.60	276.7	205.5	235.1	-	170.4	279.6	209.2	238	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400C9-52AXSP04	192.50	319.1	239.3	272.4	547.7	199.6	322.6	243.5	275.9	547.5	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400C9-532AXSP04	181.70	305.1	227.6	259.5	527.9	188.7	308.1	231.9	263	527.2	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400C9-62AXSP06	222.20	347.5	265.8	298.8	-	225.9	348.8	268.1	300.2	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400C9-632AXSP06	214.40	338.4	258	290.6	-	217.8	340	259.7	291.9	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400K3-42AXSP04	173.50	288.7	215.2	245.7	-	179.2	291.1	218.7	248.2	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400K3-432AXSP04	160.10	269.7	200.2	229.1	-	165.7	272.4	203.6	231.5	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400K3-52AXSP04	190.10	314.8	236.2	268.8	539.9	196.8	317.7	240	271.8	538.8	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400K3-532AXSP04	178.00	299.1	223.3	254.5	516.8	184.6	301.6	226.9	257.2	515.6	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400K3-62AXSP06	221.80	346.3	265.3	298.2	-	224.9	346.7	266.4	298.4	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400K3-632AXSP06	212.10	334.4	254.7	287.3	-	215.1	334.9	256.4	287.6	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400K9-42AXSP04	173.50	288.7	215.2	245.7	-	179.2	291.1	218.7	248.2	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400K9-432AXSP04	160.10	269.7	200.2	229.1	-	165.7	272.4	203.6	231.5	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400K9-52AXSP04	190.10	314.8	236.2	268.8	539.9	196.8	317.7	240	271.8	538.8	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400K9-532AXSP04	190.10	314.8	236.2	268.8	539.9	196.8	317.7	240	271.8	538.8	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400K9-532AXSP04	178.00	299.1	223.3	254.5	516.8	184.6	301.6	226.9	257.2	515.6	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400K9-62AXSP06	221.80	346.3	265.3	298.2	-	224.9	346.7	266.4	298.4	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400K9-632AXSP06	212.10	334.4	254.7	287.3	-	215.1	334.9	256.4	287.6	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400R3-42AXSP04	175.50	291.7	217.5	248.1	-	181.1	294.8	220.9	250.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400R3-432AXSP04	162.00	272.6	202.4	231.7	-	167.7	275.3	205.7	234.3	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB400R3-52AXSP04	191.90	318	238.5	271.4	545.7	198.8	321	242.5	274.1	544	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400R3-532AXSP04	179.90	302	225.8	257.4	522.1	186.7	304.7	229.1	260.2	521.2	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB400R3-62AXSP06	223.80	349.6	267.7	300.5	-	226.6	350	269	301.2	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB400R3-632AXSP06	214.10	337.8	257.1	289.6	-	216.8	338.4	258.5	290.6	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB50B3-42AXSP04	183.30	305	227.1	259.1	-	189.6	308.5	231.3	262.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB50B3-432AXSP04	170.50	286.5	212.8	243.3	-	176.7	290	216.7	246.5	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB50B3-52AXSP02	-	-	-	-	-	-	-	-	-	-	676	10.8	(2) 4"	541	7.1	(2) 4"	812	15.2	(2) 4"
EAW-FD155SPB50B3-532AXSP04	-	-	-	-	-	194.8	317.9	238.9	271.1	544	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB50B3-62AXSP02	-	-	-	-	-	-	-	-	-	-	812	12	(2) 4"	649	7.9	(2) 4"	974	13.7	(3) 4"
EAW-FD155SPB50B3-632AXSP04	-	-	-	-	-	-	-	-	-	-	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550C2-42AXSP04	196.10	326.6	243	277.6	-	202.4	330.3	247.5	281.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C2-432AXSP04	181.70	304.5	225.9	258.6	-	187.6	308.1	230	261.9	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C2-52AXSP04	214.80	354.9	265.7	302.6	-	222.8	358.8	270.4	306.4	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C2-532AXSP04	201.70	336.9	251.4	286.7	-	209.1	340.8	256	290.6	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C2-632AXSP04	-	-	-	-	-	223.7	363.2	274.2	310.3	616.8	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550C3-42AXSP04	196.10	326.6	243	277.6	-	202.4	330.3	247.5	281.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C3-432AXSP04	181.70	304.5	225.9	258.6	-	187.6	308.1	230	261.9	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C3-52AXSP04	214.80	354.9	265.7	302.6	-	222.8	358.8	270.4	306.4	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C3-532AXSP04	201.70	336.9	251.4	286.7	-	209.1	340.8	256	290.6	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C3-62AXSP02	-	-	-	-	-	223.7	363.2	274.2	310.3	616.8	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550C3-632AXSP04	196.10	326.6	243	277.6	-	202.4	330.3	247.5	281.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C4-42AXSP04	181.70	304.5	225.9	258.6	-	187.6	308.1	230	261.9	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C4-52AXSP04	214.80	354.9	265.7	302.6	-	222.8	358.8	270.4	306.4	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C4-532AXSP04	201.70	336.9	251.4	286.7	-	209.1	340.8	256	290.6	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C4-632AXSP04	-	-	-	-	-	223.7	363.2	274.2	310.3	616.8	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550C5-42AXSP04	196.10	326.6	243	277.6	-	202.4	330.3	247.5	281.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C5-432AXSP04	181.70	304.5	225.9	258.6	-	187.6	308.1	230	261.9	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550C5-52AXSP04	214.80	354.9	265.7	302.6	-	222.8	358.8	270.4	306.4	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C5-532AXSP04	201.70	336.9	251.4	286.7	-	209.1	340.8	256	290.6	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550C5-632AXSP04	-	-	-	-	-	223.7	363.2	274.2	310.3	616.8	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550C8-42AXSP04	196.10																		

EAW-FD155SPB550K8-425AXSP04	188.80	313.9	233.9	267.2	-	194.8	317.2	237.8	270.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550K8-432AXSP04	174.60	292.7	217.3	248.6	-	180.3	295.9	221	251.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550K8-525AXSP04	207.30	343	256.8	292.2	-	214.5	346.4	261.1	295.6	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550K8-532AXSP04	194.10	325.1	242.4	276.9	563.6	201.3	328.6	246.5	280	562.4	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550K8-625AXSP04	219.20	361.1	271.9	308.6	614.4	227.2	364.4	276.5	312	613	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550K8-632AXSP06	230.10	364	276.7	312.1	-	233.1	364.7	278.2	313	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB550K9-425AXSP04	188.80	313.9	233.9	267.2	-	194.8	317.2	237.8	270.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550K9-432AXSP04	174.60	292.7	217.3	248.6	-	180.3	295.9	221	251.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550K9-525AXSP04	207.30	343	256.8	292.2	-	214.5	346.4	261.1	295.6	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550K9-532AXSP04	194.10	325.1	242.4	276.9	563.6	201.3	328.6	246.5	280	562.4	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550K9-625AXSP04	219.20	361.1	271.9	308.6	614.4	227.2	364.4	276.5	312	613	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550K9-632AXSP06	230.10	364	276.7	312.1	-	233.1	364.7	278.2	313	-	270	25.8	4"	216	19.4	3"	325	36.2	4"
EAW-FD155SPB550R3-425AXSP04	192.20	320.1	238	272.1	-	198.2	323	242.2	275.4	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550R3-432AXSP04	177.80	298	221.2	253	-	183.6	301.1	224.9	256.2	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB550R3-525AXSP04	211.20	348.7	261.3	297.4	-	218.6	352.3	265.8	301.1	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550R3-532AXSP04	197.80	330.4	246.5	281.3	-	204.9	334.4	251.1	284.8	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB550R3-625AXSP04	223.10	367.4	276.5	313.9	625.6	231.4	371	281.3	317.5	624.4	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB550R3-632AXSP04	211.50	353.5	264.7	301.5	606.6	220	356.8	269.5	304.9	606.3	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K2-425AXSP04	198.30	330.2	245.6	280.6	-	204.8	334.2	250.2	284.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K2-432AXSP04	183.50	308	228.3	261.4	-	189.6	311.3	232.5	264.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K2-525AXSP04	217.70	359.1	268.6	306	-	225.4	363.4	273.7	310.2	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K2-532AXSP04	203.90	340.5	253.9	290.2	-	211.4	344.6	258.7	293.7	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K2-625AXSP04	229.80	377.9	284.5	323.1	644.1	238.3	382.1	289.4	326.8	643.7	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K2-632AXSP04	218.20	363.5	272.3	310.3	625.6	226.4	368	277.1	314.2	625.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K3-425AXSP04	198.30	330.2	245.6	280.6	-	204.8	334.2	250.2	284.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K3-432AXSP04	183.50	308	228.3	261.4	-	189.6	311.3	232.5	264.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K3-525AXSP04	217.70	359.1	268.6	306	-	225.4	363.4	273.7	310.2	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K3-532AXSP04	203.90	340.5	253.9	290.2	-	211.4	344.6	258.7	293.7	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K3-625AXSP04	229.80	377.9	284.5	323.1	644.1	238.3	382.1	289.4	326.8	643.7	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K3-632AXSP04	218.20	363.5	272.3	310.3	625.6	226.4	368	277.1	314.2	625.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K4-425AXSP04	198.30	330.2	245.6	280.6	-	204.8	334.2	250.2	284.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K4-432AXSP04	183.50	308	228.3	261.4	-	189.6	311.3	232.5	264.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K4-525AXSP04	217.70	359.1	268.6	306	-	225.4	363.4	273.7	310.2	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K4-532AXSP04	203.90	340.5	253.9	290.2	-	211.4	344.6	258.7	293.7	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K4-625AXSP04	229.80	377.9	284.5	323.1	644.1	238.3	382.1	289.4	326.8	643.7	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K4-632AXSP04	218.20	363.5	272.3	310.3	625.6	226.4	368	277.1	314.2	625.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K5-425AXSP04	198.30	330.2	245.6	280.6	-	204.8	334.2	250.2	284.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K5-432AXSP04	183.50	308	228.3	261.4	-	189.6	311.3	232.5	264.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K5-525AXSP04	217.70	359.1	268.6	306	-	225.4	363.4	273.7	310.2	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K5-532AXSP04	203.90	340.5	253.9	290.2	-	211.4	344.6	258.7	293.7	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K5-625AXSP04	229.80	377.9	284.5	323.1	644.1	238.3	382.1	289.4	326.8	643.7	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K5-632AXSP04	218.20	363.5	272.3	310.3	625.6	226.4	368	277.1	314.2	625.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K8-425AXSP04	198.30	330.2	245.6	280.6	-	204.8	334.2	250.2	284.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K8-432AXSP04	183.50	308	228.3	261.4	-	189.6	311.3	232.5	264.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K8-525AXSP04	217.70	359.1	268.6	306	-	225.4	363.4	273.7	310.2	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K8-532AXSP04	203.90	340.5	253.9	290.2	-	211.4	344.6	258.7	293.7	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K8-625AXSP04	229.80	377.9	284.5	323.1	644.1	238.3	382.1	289.4	326.8	643.7	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K8-632AXSP04	218.20	363.5	272.3	310.3	625.6	226.4	368	277.1	314.2	625.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K9-425AXSP04	198.30	330.2	245.6	280.6	-	204.8	334.2	250.2	284.6	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K9-432AXSP04	183.50	308	228.3	261.4	-	189.6	311.3	232.5	264.8	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750K9-525AXSP04	217.70	359.1	268.6	306	-	225.4	363.4	273.7	310.2	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K9-625AXSP04	203.90	340.5	253.9	290.2	-	211.4	344.6	258.7	293.7	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750K9-632AXSP04	229.80	377.9	284.5	323.1	644.1	238.3	382.1	289.4	326.8	643.7	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750K9-632AXSP04	218.20	363.5	272.3	310.3	625.6	226.4	368	277.1	314.2	625.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750R3-425AXSP04	194.40	323.5	240.9	275.4	-	200.9	327.8	245.3	279.1	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750R3-432AXSP04	180.30	302.2	224.1	256.4	-	186.1	305.7	228.1	259.9	-	270	17.8	4"	216	14.1	3"	325	25	4"
EAW-FD155SPB750R3-525AXSP04	213.30	352.4	263.5	300	-	220.6	356.4	268.3	304	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750R3-532AXSP04	199.90	334.5	249.2	284.7	-	207.3	338.3	253.7	288	-	338	18.8	4"	270	12.4	4"	406	26.4	4"
EAW-FD155SPB750R3-625AXSP04	224.70	370.3	278.5	316.2	630.7	233.4	374.3	283.8	320.3	630.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SPB750R3-632AXSP04	213.90	356.4	267.3	304.4	612.9	222.2	360.7	271.9	308.1	612.2	406	20	4"	325	13.2	4"	487	23.8	(2) 4"
EAW-FD155SZB370C2-425AXSP04	192.70	320.6	239.1	272.9	-	199.2	323.9	243.1	275.8	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB370C2-432AXSP04	178.20	300.1	223	254.8	-	184.2	302.8	226.3	257.5	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB370C2-525AXSP04	209.40	347.1	260.1	295.9	595.2	217	350.6	264.5	299.5	593.7	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB370C2-532AXSP04	196.80	330.7	247	281.5	571.4	204.1	333.7	251.1	284.6	570.3	378	19.5	4"	302					

EAW-FD155S2B370K5-632AXSP06	230.00	361.9	276	310.7	-	232.8	361.8	276.9	311	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B370K8-425AXSP04	187.10	311.7	232.5	265.1	-	193.2	314.3	235.9	267.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B370K8-432AXSP04	172.60	291	216.2	247.3	507.6	178.5	293.3	219.6	249.7	505.5	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B370K8-525AXSP04	204.30	339.3	254.5	289.4	581.2	211.4	341.7	258.1	292.1	578.9	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B370K8-532AXSP06	212.50	338.3	256.5	290.2	-	215.4	338.7	257.8	290.4	-	254	28.9	3"	203	19.1	3"	304	35.9	4"
EAW-FD155S2B370K8-625AXSP06	240.80	375.3	287.4	322.9	-	243.7	375.7	288.7	323.2	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B370K8-632AXSP06	230.00	361.9	276	310.7	-	232.8	361.8	276.9	311	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400R3-425AXSP04	185.70	309.3	231	263.6	-	192.3	312.6	234.7	266.5	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400R3-432AXSP04	172.10	290.3	215.9	246.7	506.4	178.4	293.1	219.5	249.6	505.2	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400R3-525AXSP04	200.50	333.2	250.2	284.4	570.4	208.2	336.8	254.5	288	569.4	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400R3-532AXSP06	211.00	335.6	254.6	287.5	-	214	336.3	256.1	288.4	-	254	28.9	3"	203	19.1	3"	304	35.9	4"
EAW-FD155S2B400R3-625AXSP06	-	-	-	-	-	-	-	-	-	-	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155S2B400R3-632AXSP06	225.80	355.5	270.9	305.3	-	229.2	356	272.6	306.1	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400C3-425AXSP04	192.70	320.6	239.1	272.9	-	199.2	323.9	243.1	275.8	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400C3-432AXSP04	178.20	300.1	223	254.8	-	184.2	302.8	226.3	257.5	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400C3-525AXSP04	209.40	347.1	260.1	295.9	595.2	217	350.6	264.5	299.5	593.7	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400C3-532AXSP04	196.80	330.7	247	281.5	571.4	204.1	333.7	251.1	284.6	570.3	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400C3-625AXSP06	244.10	381.3	291.9	328	-	247.9	381.9	293.7	328.9	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400C3-632AXSP06	234.70	370.4	282.2	317.8	-	238.2	370.7	283.5	318.4	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400C3-625AXSP06	192.70	320.6	239.1	272.9	-	199.2	323.9	243.1	275.8	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400C3-432AXSP04	178.20	300.1	223	254.8	-	184.2	302.8	226.3	257.5	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400C3-525AXSP04	209.40	347.1	260.1	295.9	595.2	217	350.6	264.5	299.5	593.7	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400C3-532AXSP04	196.80	330.7	247	281.5	571.4	204.1	333.7	251.1	284.6	570.3	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400C3-625AXSP06	244.10	381.3	291.9	328	-	247.9	381.9	293.7	328.9	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400C3-632AXSP06	234.70	370.4	282.2	317.8	-	238.2	370.7	283.5	318.4	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400R3-425AXSP04	187.10	311.7	232.5	265.1	-	193.2	314.3	235.9	267.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400K3-432AXSP04	172.60	291	216.2	247.3	507.6	178.5	293.3	219.6	249.7	505.5	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400K3-528AXSP04	204.30	339.3	254.5	289.4	581.2	211.4	341.7	258.1	292.1	578.9	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400K3-532AXSP06	212.50	338.3	256.5	290.2	-	215.4	338.7	257.8	290.4	-	254	28.9	3"	203	19.1	3"	304	35.9	4"
EAW-FD155S2B400K3-625AXSP06	240.80	375.3	287.4	322.9	-	243.7	375.7	288.7	323.2	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400K3-632AXSP06	230.00	361.9	276	310.7	-	232.8	361.8	276.9	311	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400K9-425AXSP04	187.10	311.7	232.5	265.1	-	193.2	314.3	235.9	267.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400K9-432AXSP04	172.60	291	216.2	247.3	507.6	178.5	293.3	219.6	249.7	505.5	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400K9-525AXSP04	204.30	339.3	254.5	289.4	581.2	211.4	341.7	258.1	292.1	578.9	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400K9-532AXSP06	212.50	338.3	256.5	290.2	-	215.4	338.7	257.8	290.4	-	254	28.9	3"	203	19.1	3"	304	35.9	4"
EAW-FD155S2B400K9-625AXSP06	240.80	375.3	287.4	322.9	-	243.7	375.7	288.7	323.2	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400K9-632AXSP06	230.00	361.9	276	310.7	-	232.8	361.8	276.9	311	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400R3-425AXSP04	189.30	315.4	235.1	268.2	-	195.5	317.7	238.7	271.2	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400R3-432AXSP04	174.70	294.4	218.8	250.1	-	180.7	297.3	222.2	252.7	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B400R3-525AXSP04	206.70	343	257.2	292.5	587.9	214.1	345.7	261.4	295.4	585.9	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B400R3-532AXSP06	215.20	342.3	259.8	293.5	-	217.9	342.8	260.9	293.9	-	254	28.9	3"	203	19.1	3"	304	35.9	4"
EAW-FD155S2B400R3-625AXSP06	242.90	379.4	290.5	326.4	-	246	379.4	291.9	326.8	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B400R3-632AXSP06	232.30	365.8	278.9	314.5	-	235.3	366.4	280.4	314.4	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B550R3-425AXSP04	200.70	333.4	248.4	283.6	-	207.2	337.1	252.8	287.2	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550R3-432AXSP04	186.00	312.5	232.1	265.5	-	192.4	315.7	236.2	268.8	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550R3-525AXSP04	216.40	358.5	269.1	305.9	615.8	224.5	363	273.9	309.8	615.5	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B550R3-532AXSP04	204.30	342.6	255.8	291.8	593.1	212.2	346.7	260.3	295.4	592.8	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B550R3-625AXSP04	-	-	-	-	-	-	-	-	-	-	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155S2B550R3-632AXSP06	-	-	-	-	-	245.8	383.8	293.1	329.5	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155S2B550C2-425AXSP04	213.60	355.7	264.7	302.5	-	220.4	359.5	269.2	306.1	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550C2-432AXSP04	197.30	331	245.6	281.1	-	203.7	334.3	249.7	284.3	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550C2-525AXSP04	234.00	386.4	289.5	329.5	-	242.3	391	294.5	333.6	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B550C2-532AXSP04	218.90	366.3	273.1	311.9	-	226.8	369.7	277.6	315.4	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B550C2-625AXSP04	247.70	408.1	307.3	348.7	694.6	257.1	412.5	313	353.1	694	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155S2B550C2-632AXSP04	235.40	393.1	294.5	335.3	675.3	244.8	397.4	299.8	339.7	674	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155S2B550C3-425AXSP04	213.60	355.7	264.7	302.5	-	220.4	359.5	269.2	306.1	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550C3-432AXSP04	197.30	331	245.6	281.1	-	203.7	334.3	249.7	284.3	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550C3-525AXSP04	234.00	386.4	289.5	329.5	-	242.3	391	294.5	333.6	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B550C3-532AXSP04	218.90	366.3	273.1	311.9	-	226.8	369.7	277.6	315.4	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155S2B550C3-625AXSP04	247.70	408.1	307.3	348.7	694.6	257.1	412.5	313	353.1	694	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155S2B550C3-632AXSP04	235.40	393.1	294.5	335.3	675.3	244.8	397.4	299.8	339.7	674	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155S2B550C4-425AXSP04	213.60	355.7	264.7	302.5	-	220.4	359.5	269.2	306.1	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550C4-432AXSP04	197.30	331	245.6	281.1	-	203.7	334.3	249.7	284.3	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155S2B550C4-525AXSP04	234.00	386.4	289.5	329.5	-	242.3	391	294.5	333										

EAW-FD155SZB550K4-625AXSP04	238.50	393.3	296.1	336.4	668.5	247.2	397.1	301.2	339.7	666.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB550K4-632AXSP06	250.60	395.7	301.2	339.5	-	253.8	396.3	302.8	340.5	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155SZB550K5-425AXSP04	204.80	340.2	253.7	289.7	-	211.1	343.9	257.7	292.8	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550K5-432AXSP04	188.90	317.3	235.6	269.6	-	195.3	320.5	239.6	272.4	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550K5-525AXSP04	224.40	371.2	278.2	316.4	-	232	374.7	282.3	320	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550K5-532AXSP04	209.60	351.1	261.9	298.8	607.8	216.9	354.4	266.3	302.3	606.7	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550K5-625AXSP04	238.50	393.3	296.1	336.4	668.5	247.2	397.1	301.2	339.7	666.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB550K5-632AXSP06	250.60	395.7	301.2	339.5	-	253.8	396.3	302.8	340.5	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155SZB550K8-425AXSP04	204.80	340.2	253.7	289.7	-	211.1	343.9	257.7	292.8	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550K8-432AXSP04	188.90	317.3	235.6	269.6	-	195.3	320.5	239.6	272.4	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550K8-525AXSP04	224.40	371.2	278.2	316.4	-	232	374.7	282.3	320	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550K8-532AXSP04	209.60	351.1	261.9	298.8	607.8	216.9	354.4	266.3	302.3	606.7	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550K8-625AXSP04	238.50	393.3	296.1	336.4	668.5	247.2	397.1	301.2	339.7	666.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB550K8-632AXSP06	250.60	395.7	301.2	339.5	-	253.8	396.3	302.8	340.5	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155SZB550K9-425AXSP04	208.80	346.9	258.5	295.2	-	215.2	350.2	262.8	298.5	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550K9-432AXSP04	192.50	323.3	240	274.5	-	199.2	326.5	243.9	277.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550K9-525AXSP04	224.40	371.2	278.2	316.4	-	232	374.7	282.3	320	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550K9-532AXSP04	209.60	351.1	261.9	298.8	607.8	216.9	354.4	266.3	302.3	606.7	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550K9-625AXSP04	238.50	393.3	296.1	336.4	668.5	247.2	397.1	301.2	339.7	666.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB550K9-632AXSP06	250.60	395.7	301.2	339.5	-	253.8	396.3	302.8	340.5	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155SZB550R3-425AXSP04	208.80	346.9	258.5	295.2	-	215.2	350.2	262.8	298.5	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550R3-432AXSP04	192.50	323.3	240	274.5	-	199.2	326.5	243.9	277.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB550R3-525AXSP04	228.70	378.3	278.3	322.3	-	236.7	382	288.1	326.2	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550R3-532AXSP04	213.60	357.7	266.8	304.8	619.9	221.2	361.3	271.2	307.9	619.1	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB550R3-625AXSP04	243.20	400.3	301.6	342.2	680.9	251.9	404.3	306.5	346.2	679.8	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB550R3-632AXSP06	254.90	403	307	346.2	-	258.4	404	308.4	346.9	-	304	26.3	4"	244	20.4	3"	365	36.9	4"
EAW-FD155SZB750K2-425AXSP04	216.10	359.8	267.6	305.9	-	222.8	363.8	272.2	309.6	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K2-432AXSP04	199.90	334.9	248.6	284.6	-	206.3	338.7	252.7	287.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K2-525AXSP04	236.70	391	292.8	333.4	-	245.1	395.3	298	337.7	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K2-532AXSP04	221.30	370.5	276	315.3	-	229.4	374	280.8	319	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K2-625AXSP04	251.30	413.8	311.3	353.4	703.6	260.2	417.9	316.9	357.6	703.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K2-632AXSP04	238.30	397.7	298.3	339.7	683.5	247.5	402.2	303.2	343.7	682.4	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K3-425AXSP04	216.10	359.8	267.6	305.9	-	222.8	363.8	272.2	309.6	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K3-432AXSP04	199.90	334.9	248.6	284.6	-	206.3	338.7	252.7	287.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K3-525AXSP04	236.70	391	292.8	333.4	-	245.1	395.3	298	337.7	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K3-532AXSP04	221.30	370.5	276	315.3	-	229.4	374	280.8	319	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K3-625AXSP04	251.30	413.8	311.3	353.4	703.6	260.2	417.9	316.9	357.6	703.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K3-632AXSP04	238.30	397.7	298.3	339.7	683.5	247.5	402.2	303.2	343.7	682.4	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K4-425AXSP04	216.10	359.8	267.6	305.9	-	222.8	363.8	272.2	309.6	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K4-432AXSP04	199.90	334.9	248.6	284.6	-	206.3	338.7	252.7	287.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K4-525AXSP04	236.70	391	292.8	333.4	-	245.1	395.3	298	337.7	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K4-532AXSP04	221.30	370.5	276	315.3	-	229.4	374	280.8	319	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K4-625AXSP04	251.30	413.8	311.3	353.4	703.6	260.2	417.9	316.9	357.6	703.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K4-632AXSP04	238.30	397.7	298.3	339.7	683.5	247.5	402.2	303.2	343.7	682.4	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K5-425AXSP04	216.10	359.8	267.6	305.9	-	222.8	363.8	272.2	309.6	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K5-432AXSP04	199.90	334.9	248.6	284.6	-	206.3	338.7	252.7	287.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K5-525AXSP04	236.70	391	292.8	333.4	-	245.1	395.3	298	337.7	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K5-532AXSP04	221.30	370.5	276	315.3	-	229.4	374	280.8	319	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K5-625AXSP04	251.30	413.8	311.3	353.4	703.6	260.2	417.9	316.9	357.6	703.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K5-632AXSP04	238.30	397.7	298.3	339.7	683.5	247.5	402.2	303.2	343.7	682.4	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K8-425AXSP04	216.10	359.8	267.6	305.9	-	222.8	363.8	272.2	309.6	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K8-432AXSP04	199.90	334.9	248.6	284.6	-	206.3	338.7	252.7	287.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K8-525AXSP04	236.70	391	292.8	333.4	-	245.1	395.3	298	337.7	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K8-532AXSP04	221.30	370.5	276	315.3	-	229.4	374	280.8	319	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K8-625AXSP04	251.30	413.8	311.3	353.4	703.6	260.2	417.9	316.9	357.6	703.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K8-632AXSP04	238.30	397.7	298.3	339.7	683.5	247.5	402.2	303.2	343.7	682.4	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K9-425AXSP04	216.10	359.8	267.6	305.9	-	222.8	363.8	272.2	309.6	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K9-432AXSP04	199.90	334.9	248.6	284.6	-	206.3	338.7	252.7	287.9	-	304	18.3	4"	244	15.1	3"	365	25.7	4"
EAW-FD155SZB750K9-525AXSP04	236.70	391	292.8	333.4	-	245.1	395.3	298	337.7	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K9-532AXSP04	221.30	370.5	276	315.3	-	229.4	374	280.8	319	-	378	19.5	4"	302	12.9	4"	453	23.7	(2) 4"
EAW-FD155SZB750K9-625AXSP04	251.30	413.8	311.3	353.4	703.6	260.2	417.9	316.9	357.6	703.3	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750K9-632AXSP04	238.30	397.7	298.3	339.7	683.5	247.5	402.2	303.2	343.7	682.4	456	17.3	(2) 4"	365	13.9	4"	548	24.2	(2) 4"
EAW-FD155SZB750R3-425AXSP04	211.80	352.3	262.4	299.7	-	218.4	356.1	267	303.3	-	304	18.3	4"	244	15.1	3"	365		

EAW-FD155SZK370K4-532AXSP04	211.10	347.7	261.5	296.8	596	217.1	349.4	264.1	298.8	592.9	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK370K4-625AXSP04	240.20	388.8	294.9	333.6	653.9	247	390.3	298.2	335.5	649.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK370K4-632AXSP04	228.20	374.3	282.1	320.4	634.9	234.8	376.1	285.2	322	631.4	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK370K5-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK370K5-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK370K5-525AXSP04	225.60	366.5	276.8	313.8	623.5	231.1	368.6	279.7	315.6	620.3	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK370K5-532AXSP04	211.10	347.7	261.5	296.8	596	217.1	349.4	264.1	298.8	592.9	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK370K5-625AXSP04	240.20	388.8	294.9	333.6	653.9	247	390.3	298.2	335.5	649.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK370K5-632AXSP04	228.20	374.3	282.1	320.4	634.9	234.8	376.1	285.2	322	631.4	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK370K8-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK370K8-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK370K8-525AXSP04	225.60	366.5	276.8	313.8	623.5	231.1	368.6	279.7	315.6	620.3	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK370K8-532AXSP04	211.10	347.7	261.5	296.8	596	217.1	349.4	264.1	298.8	592.9	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK370K8-625AXSP04	240.20	388.8	294.9	333.6	653.9	247	390.3	298.2	335.5	649.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK370K8-632AXSP04	228.20	374.3	282.1	320.4	634.9	234.8	376.1	285.2	322	631.4	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400B3-425AXSP04	205.30	336.4	252.1	286.8	-	210.4	338	255	288.7	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400B3-432AXSP04	190.50	314.9	235.3	268.4	-	195.6	316.7	238.2	270.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400B3-525AXSP04	223.40	363.4	274.5	311.1	617.9	229.8	365.7	277.5	313.2	615.4	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400B3-532AXSP04	210.50	346.9	260.5	296.1	594.5	216.7	348.7	263.6	298.2	591.7	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400B3-625AXSP04	235.50	382	289.1	327.5	641.3	243	384.3	293.3	329.9	638.4	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400B3-632AXSP06	247.40	386	295.6	332.4	-	249.8	386.3	296.4	332	-	304	28.8	4"	244	22.1	3"	365	40.4	4"
EAW-FD155SZK400C3-425AXSP04	212.40	348	260.8	296.3	-	217.3	350	263.6	298.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400C3-432AXSP04	196.40	324.3	242.4	276.4	-	201.6	326.8	245.2	278.3	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400C3-525AXSP04	232.60	378	285.1	322.8	-	238.7	380.2	288.1	325.2	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400C3-532AXSP04	218.30	359	269.6	306.2	616.4	224.1	360.9	272.9	308.9	613.4	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400C3-625AXSP04	246.40	398.8	302.2	341.5	670.3	253.4	400.9	306	344.4	667.6	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400C3-632AXSP04	235.00	385.5	290.6	329.8	654.7	242.2	387.4	293.9	332	651.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400C9-425AXSP04	212.40	348	260.8	296.3	-	217.3	350	263.6	298.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400C9-432AXSP04	196.40	324.3	242.4	276.4	-	201.6	326.8	245.2	278.3	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400C9-525AXSP04	232.60	378	285.1	322.8	-	238.7	380.2	288.1	325.2	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400C9-532AXSP04	218.30	359	269.6	306.2	616.4	224.1	360.9	272.9	308.9	613.4	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400C9-625AXSP04	246.40	398.8	302.2	341.5	670.3	253.4	400.9	306	344.4	667.6	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400C9-632AXSP04	235.00	385.5	290.6	329.8	654.7	242.2	387.4	293.9	332	651.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K3-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K3-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K3-525AXSP04	225.60	366.5	276.8	313.8	623.5	231.1	368.6	279.7	315.6	620.3	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K3-532AXSP04	211.10	347.7	261.5	296.8	596	217.1	349.4	264.1	298.8	592.9	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K3-625AXSP04	240.20	388.8	294.9	333.6	653.9	247	390.3	298.2	335.5	649.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K3-632AXSP04	228.20	374.3	282.1	320.4	634.9	234.8	376.1	285.2	322	631.4	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K9-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K9-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K9-525AXSP04	232.60	378	285.1	322.8	-	238.7	380.2	288.1	325.2	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K9-532AXSP04	218.30	359	269.6	306.2	616.4	224.1	360.9	272.9	308.9	613.4	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K9-625AXSP04	246.40	398.8	302.2	341.5	670.3	253.4	400.9	306	344.4	667.6	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K9-632AXSP04	235.00	385.5	290.6	329.8	654.7	242.2	387.4	293.9	332	651.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K3-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K3-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K3-525AXSP04	225.60	366.5	276.8	313.8	623.5	231.1	368.6	279.7	315.6	620.3	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K3-532AXSP04	211.10	347.7	261.5	296.8	596	217.1	349.4	264.1	298.8	592.9	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K3-625AXSP04	240.20	388.8	294.9	333.6	653.9	247	390.3	298.2	335.5	649.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K3-632AXSP04	228.20	374.3	282.1	320.4	634.9	234.8	376.1	285.2	322	631.4	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K9-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K9-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K9-525AXSP04	232.60	378	285.1	322.8	-	238.7	380.2	288.1	325.2	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K9-532AXSP04	218.30	359	269.6	306.2	616.4	224.1	360.9	272.9	308.9	613.4	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K9-625AXSP04	246.40	398.8	302.2	341.5	670.3	253.4	400.9	306	344.4	667.6	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K9-632AXSP04	235.00	385.5	290.6	329.8	654.7	242.2	387.4	293.9	332	651.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K3-425AXSP04	205.60	336.3	252.4	287.2	-	210.4	338.3	254.9	289	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K3-432AXSP04	189.80	313.8	234.5	267.4	-	194.7	315.7	237.1	269.1	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK400K3-525AXSP04	225.60	366.5	276.8	313.8	623.5	231.1	368.6	279.7	315.6	620.3	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K3-532AXSP04	211.10	347.7	261.5	296.8	596	217.1	349.4	264.1	298.8	592.9	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK400K3-625AXSP04	240.20	388.8	294.9	333.6	653.9	247	390.3	298.2	335.5	649.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK400K3-632AXSP04	228.20	374.3	282.1	320.4	634.9	234.8	376.1	285.2	322	631.4	456	18.9	(2) 4"	365	15				

EAW-FD155SZK550K3-525AXSP04	248.40	403.2	303.2	344.4	-	254.2	405.1	307.1	346.6	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K3-532AXSP04	232.00	381	285.7	325.5	-	238.3	384	289.5	327.5	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K3-625AXSP04	265.10	428	324.1	366.6	722	272	430.4	327.8	369.3	718.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K3-632AXSP04	251.10	410.9	309.9	351.5	699.6	258.1	413.1	313.6	354	695.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K4-425AXSP04	225.20	369.5	276.6	314.6	-	230.6	372.1	279.9	317.4	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K4-432AXSP04	208.00	343.7	256.7	292.5	-	213.1	345.8	259.6	294.7	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K4-525AXSP04	248.40	403.2	303.2	344.4	-	254.2	405.1	307.1	346.6	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K4-532AXSP04	232.00	381	285.7	325.5	-	238.3	384	289.5	327.5	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K4-625AXSP04	265.10	428	324.1	366.6	722	272	430.4	327.8	369.3	718.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K4-632AXSP04	251.10	410.9	309.9	351.5	699.6	258.1	413.1	313.6	354	695.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K5-425AXSP04	225.20	369.5	276.6	314.6	-	230.6	372.1	279.9	317.4	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K5-432AXSP04	208.00	343.7	256.7	292.5	-	213.1	345.8	259.6	294.7	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K5-525AXSP04	248.40	403.2	303.2	344.4	-	254.2	405.1	307.1	346.6	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K5-532AXSP04	232.00	381	285.7	325.5	-	238.3	384	289.5	327.5	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K5-625AXSP04	265.10	428	324.1	366.6	722	272	430.4	327.8	369.3	718.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K5-632AXSP04	251.10	410.9	309.9	351.5	699.6	258.1	413.1	313.6	354	695.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K8-425AXSP04	225.20	369.5	276.6	314.6	-	230.6	372.1	279.9	317.4	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K8-432AXSP04	208.00	343.7	256.7	292.5	-	213.1	345.8	259.6	294.7	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K8-525AXSP04	248.40	403.2	303.2	344.4	-	254.2	405.1	307.1	346.6	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K8-532AXSP04	232.00	381	285.7	325.5	-	238.3	384	289.5	327.5	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K8-625AXSP04	265.10	428	324.1	366.6	722	272	430.4	327.8	369.3	718.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K8-632AXSP04	251.10	410.9	309.9	351.5	699.6	258.1	413.1	313.6	354	695.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K9-425AXSP04	225.20	369.5	276.6	314.6	-	230.6	372.1	279.9	317.4	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K9-432AXSP04	208.00	343.7	256.7	292.5	-	213.1	345.8	259.6	294.7	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550K9-525AXSP04	248.40	403.2	303.2	344.4	-	254.2	405.1	307.1	346.6	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K9-532AXSP04	232.00	381	285.7	325.5	-	238.3	384	289.5	327.5	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550K9-625AXSP04	265.10	428	324.1	366.6	722	272	430.4	327.8	369.3	718.2	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550K9-632AXSP04	251.10	410.9	309.9	351.5	699.6	258.1	413.1	313.6	354	695.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550R3-425AXSP04	229.50	376.7	282.2	321.1	-	235.3	379.6	285.7	323.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550R3-432AXSP04	212.30	350.8	261.9	298.6	-	217.4	353.3	265	301	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK550R3-525AXSP04	253.10	411	309.8	351.3	-	259.3	413.7	313.4	353.8	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550R3-532AXSP04	236.90	388.9	291.8	332	-	243.3	391.4	295.3	334.2	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK550R3-625AXSP04	270.50	436.6	330.9	374.4	737.1	277.8	439.4	334.4	376.8	733.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK550R3-632AXSP04	256.20	419.1	315.9	358.4	714.3	263.6	421.6	319.8	361.1	710.8	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750C4-425AXSP04	245.40	403.6	301.7	343.8	-	251.5	407	305.9	346.8	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750C4-432AXSP04	226.70	375.6	280	319.5	-	232.7	378.6	283.6	322.5	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750C4-525AXSP04	269.70	439.2	330	374.8	-	276.8	442.2	334.5	378	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750C4-532AXSP04	253.20	415.2	311.2	354.4	-	260.1	419.1	315.6	357.8	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750C4-632AXSP04	273.10	446.5	336.1	381.2	761.9	281.5	449.9	340.8	384.7	760.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750C5-425AXSP04	245.40	403.6	301.7	343.8	-	251.5	407	305.9	346.8	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750C5-432AXSP04	226.70	375.6	280	319.5	-	232.7	378.6	283.6	322.5	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750C5-525AXSP04	269.70	439.2	330	374.8	-	276.8	442.2	334.5	378	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750C5-532AXSP04	253.20	415.2	311.2	354.4	-	260.1	419.1	315.6	357.8	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750C5-632AXSP04	273.10	446.5	336.1	381.2	761.9	281.5	449.9	340.8	384.7	760.5	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K2-425AXSP04	238.30	391.7	293	333.6	-	244.2	394.6	296.8	336.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K2-432AXSP04	220.50	365.1	272.1	310.6	-	225.9	367.4	275.5	312.9	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K2-525AXSP04	262.40	427.2	320.9	364.9	-	269.2	430	325.1	367.9	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750K2-532AXSP04	246.10	403.7	302.4	344.2	-	252.7	406.9	306.3	347	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750K2-625AXSP04	280.50	452.9	342.7	387.4	-	288.3	456.1	347.2	390.8	-	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K2-632AXSP04	266.30	435.2	327.4	371.8	741.7	273.8	437.6	331.9	374.5	738.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K3-425AXSP04	238.30	391.7	293	333.6	-	244.2	394.6	296.8	336.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K3-432AXSP04	220.50	365.1	272.1	310.6	-	225.9	367.4	275.5	312.9	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K3-525AXSP04	262.40	427.2	320.9	364.9	-	269.2	430	325.1	367.9	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750K3-532AXSP04	246.10	403.7	302.4	344.2	-	252.7	406.9	306.3	347	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750K3-625AXSP04	280.50	452.9	342.7	387.4	-	288.3	456.1	347.2	390.8	-	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K3-632AXSP04	266.30	435.2	327.4	371.8	741.7	273.8	437.6	331.9	374.5	738.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K4-425AXSP04	238.30	391.7	293	333.6	-	244.2	394.6	296.8	336.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K4-432AXSP04	220.50	365.1	272.1	310.6	-	225.9	367.4	275.5	312.9	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K4-525AXSP04	262.40	427.2	320.9	364.9	-	269.2	430	325.1	367.9	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750K4-532AXSP04	246.10	403.7	302.4	344.2	-	252.7	406.9	306.3	347	-	378	21.2	4"	302	14	4"	453	26	(2) 4"
EAW-FD155SZK750K4-625AXSP04	280.50	452.9	342.7	387.4	-	288.3	456.1	347.2	390.8	-	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K4-632AXSP04	266.30	435.2	327.4	371.8	741.7	273.8	437.6	331.9	374.5	738.9	456	18.9	(2) 4"	365	15	4"	548	26.6	(2) 4"
EAW-FD155SZK750K5-425AXSP04	238.30	391.7	293	333.6	-	244.2	394.6	296.8	336.6	-	304	19.9	4"	244	16.2	3"	365	28	4"
EAW-FD155SZK750K5-432AXSP04	220.50	365.1	272.1	310.6	-	225.9	367.4	275.5	312.9	-	304	19.9	4"	244	16.2	3"	365	28	4

EAW-FD1556PB400C9-532AXSP04	230.10	373.9	281.3	319.1	-	235.4	376	284.7	321.4	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400C9-625AXSP04	255.10	406.9	309	348.8	-	261.7	410.2	313.3	352.2	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400C9-632AXSP04	245.40	395.9	299.5	338.9	671.6	251.8	399.1	303.2	342.2	670	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400K3-425AXSP04	217.10	353.5	265.5	301.8	-	221.7	355.6	268.4	303.6	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB400K3-432AXSP04	201.40	330.3	247.3	281.6	-	206	332.1	249.9	283.5	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB400K3-525AXSP04	239.50	385.5	291.5	330.1	-	244.8	387.6	294.4	332	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400K3-532AXSP04	225.80	366.4	275.3	312.8	-	230.4	368.1	278.5	314.8	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400K3-625AXSP04	254.30	406.1	308.4	348.1	-	260.2	407.7	311.4	350	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400K3-632AXSP04	242.30	391.3	296.1	335	663.4	248.3	393.2	299.3	337.2	659.8	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400K9-425AXSP04	217.10	353.5	265.5	301.8	-	221.7	355.6	268.4	303.6	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB400K9-432AXSP04	201.40	330.3	247.3	281.6	-	206	332.1	249.9	283.5	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB400K9-525AXSP04	239.50	385.5	291.5	330.1	-	244.8	387.6	294.4	332	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400K9-532AXSP04	225.80	366.4	275.3	312.8	-	230.4	368.1	278.5	314.8	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400K9-625AXSP04	254.30	406.1	308.4	348.1	-	260.2	407.7	311.4	350	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400K9-632AXSP04	242.30	391.3	296.1	335	663.4	248.3	393.2	299.3	337.2	659.8	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400R3-425AXSP04	219.40	357.8	268.4	304.8	-	224.1	359.5	271.1	307.3	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB400R3-432AXSP04	203.50	334.2	250	284.5	-	208	335.8	252.8	286.6	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB400R3-525AXSP04	241.80	389.4	293.9	332.9	-	247.3	391.8	297.5	335.5	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400R3-532AXSP04	228.00	370	278.4	315.8	-	233	371.9	281.2	318	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB400R3-625AXSP04	256.90	409.3	311.2	351.3	-	262.6	411.7	314.3	353.4	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB400R3-632AXSP04	244.60	395.1	298.9	338.3	669.3	250.7	397.2	301.8	340.6	666.8	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550B3-425AXSP02	-	324.6	223.8	268.1	596.8	-	336.3	238.7	279.8	601.7	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550B3-432AXSP04	213.70	351.1	262.4	299	-	218.9	354.1	266.1	301.7	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB550B3-525AXSP02	-	-	-	-	-	-	-	-	-	-	676	12.3	(2) 4"	541	8.1	(2) 4"	812	17.3	(2) 4"
EAW-FD1556PB550B3-532AXSP04	-	-	-	-	-	242.5	388.1	293.4	332	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.8	(3) 4"
EAW-FD1556PB550B3-632AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.8	(3) 4"
EAW-FD1556PB550C3-425AXSP02	-	349.4	241.4	288.6	640.8	192.5	361	256.5	300.7	645.7	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550C3-432AXSP02	-	323.5	221.8	266.5	600.3	-	334.8	236.3	278.1	604.5	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550C3-525AXSP04	269.00	434.4	327.8	371.4	-	275.5	438.2	332.1	374.7	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550C3-532AXSP04	253.60	413.3	310.1	352.1	-	259.5	416.3	314.1	355.4	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550C3-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.8	(3) 4"
EAW-FD1556PB550C3-632AXSP04	-	-	-	-	-	279	443.4	335.9	379.2	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550C9-425AXSP02	-	349.4	241.4	288.6	640.8	192.5	361	256.5	300.7	645.7	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550C9-432AXSP02	-	323.5	221.8	266.5	600.3	-	334.8	236.3	278.1	604.5	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550C9-525AXSP04	269.00	434.4	327.8	371.4	-	275.5	438.2	332.1	374.7	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550C9-532AXSP04	253.60	413.3	310.1	352.1	-	259.5	416.3	314.1	355.4	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550C9-625AXSP02	-	-	-	-	-	-	-	-	-	-	812	13.5	(2) 4"	649	8.8	(2) 4"	974	15.8	(3) 4"
EAW-FD1556PB550C9-632AXSP04	-	-	-	-	-	279	443.4	335.9	379.2	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550K3-425AXSP02	-	335.2	231.3	277.1	616.2	184.2	346.3	245.8	288.1	619.3	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550K3-432AXSP04	218.40	358.8	268.4	305.6	-	223.2	361.4	271.5	308.1	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB550K3-525AXSP04	260.10	419.7	316.6	359.2	-	266.1	422.9	320.6	362	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550K3-532AXSP04	244.60	398.6	299.3	340.1	-	250.2	400.6	302.9	342.4	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550K3-625AXSP04	276.80	442.1	335.3	378.9	-	283	444.7	339.1	381.7	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550K3-632AXSP04	263.90	425.5	321.4	364.2	-	270.1	428.4	325.1	366.7	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550K9-425AXSP02	-	335.2	231.3	277.1	616.2	184.2	346.3	245.8	288.1	619.3	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550K9-432AXSP04	218.40	358.8	268.4	305.6	-	223.2	361.4	271.5	308.1	-	270	20.8	4"	216	16.1	3"	325	29.1	4"
EAW-FD1556PB550K9-525AXSP04	260.10	419.7	316.6	359.2	-	266.1	422.9	320.6	362	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550K9-532AXSP04	244.60	398.6	299.3	340.1	-	250.2	400.6	302.9	342.4	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550K9-625AXSP04	276.80	442.1	335.3	378.9	-	283	444.7	339.1	381.7	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550K9-632AXSP04	263.90	425.5	321.4	364.2	-	270.1	428.4	325.1	366.7	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550R3-425AXSP02	-	341.8	236.1	282.3	627.5	188	352.7	250.5	293.8	631	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550R3-432AXSP02	-	315.9	216.2	260.3	586.9	-	326.9	231	271.5	590.3	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB550R3-525AXSP04	264.50	427.4	322.2	365	-	270.8	430.2	325.8	368.1	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550R3-532AXSP04	248.70	405.1	304.4	345.4	-	254.5	407.7	307.9	348.9	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB550R3-625AXSP04	281.40	449.9	341	385.4	-	287.9	452.8	345.1	388.5	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB550R3-632AXSP04	268.30	433	326.8	369.8	-	274.8	435.5	330.7	373.2	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB750K3-425AXSP02	-	353.5	244.3	292.2	648.3	195	365	259.7	304.2	653.5	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB750K3-432AXSP02	-	327.4	224.2	269.6	606.8	-	338.6	239	281.1	610.8	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB750K3-525AXSP04	272.40	440.3	331.4	376.4	-	278.8	443.8	336.2	379.4	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB750K3-532AXSP04	256.00	417.8	313.3	356.5	-	262.4	421	317.5	359.3	-	338	21.8	4"	270	14.4	4"	406	30.6	4"
EAW-FD1556PB750K3-625AXSP04	289.50	462.8	350.4	396.2	-	296.1	465.8	355.1	399.9	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB750K3-632AXSP04	275.80	445.4	336.3	380.7	-	282.4	448.6	340.2	384.1	-	406	23	4"	325	15.1	4"	487	28	(2) 4"
EAW-FD1556PB750K3-625AXSP02	-	353.5	244.3	292.2	648.3	195	365	259.7	304.2	653.5	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB750K9-432AXSP02	-	327.4	224.2	269.6	606.8	-	338.6	239	281.1	610.8	541	11.2	(2) 4"	433	10.8	4"	649	15.8	(2) 4"
EAW-FD1556PB750K9-525AXSP04	272.40	440.3	331.4	376.4</															

EAW-FD1556ZB370K2-525AXSP04	258.20	415.4	314	355.4	-	263.8	416.9	316.5	357.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB370K2-532AXSP04	242.50	394	296.6	336.7	-	248	396	299.5	338.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB370K2-625AXSP04	275.70	439.5	334.3	377.1	736.9	281.7	441.4	337.5	379.2	733.1	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB370K2-632AXSP04	262.10	423.6	320.6	362.5	717.1	268.5	425.5	323.4	364.7	712	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB370K4-425AXSP04	234.70	381.4	286.5	325.5	-	239.4	383.8	289.8	327.5	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB370K4-432AXSP04	217.60	356.8	266.9	303.9	-	222	358.1	269.6	305.6	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB370K4-525AXSP04	258.20	415.4	314	355.4	-	263.8	416.9	316.5	357.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB370K4-532AXSP04	242.50	394	296.6	336.7	-	248	396	299.5	338.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB370K4-625AXSP04	275.70	439.5	334.3	377.1	736.9	281.7	441.4	337.5	379.2	733.1	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB370K4-632AXSP04	262.10	423.6	320.6	362.5	717.1	268.5	425.5	323.4	364.7	712	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB370K5-425AXSP04	234.70	381.4	286.5	325.5	-	239.4	383.8	289.8	327.5	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB370K5-432AXSP04	217.60	356.8	266.9	303.9	-	222	358.1	269.6	305.6	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB370K5-525AXSP04	258.20	415.4	314	355.4	-	263.8	416.9	316.5	357.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB370K5-532AXSP04	242.50	394	296.6	336.7	-	248	396	299.5	338.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB370K5-625AXSP04	275.70	439.5	334.3	377.1	736.9	281.7	441.4	337.5	379.2	733.1	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB370K5-632AXSP04	262.10	423.6	320.6	362.5	717.1	268.5	425.5	323.4	364.7	712	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400B3-425AXSP04	232.20	379.2	284.9	323.6	-	238.4	381.7	288.3	325.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400B3-432AXSP04	217.10	355.9	266.5	303.4	-	222.2	357.9	269.5	305.4	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400B3-525AXSP04	253.80	407.9	308.6	349.2	-	259.7	410.8	312.1	351.7	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400B3-532AXSP04	240.20	390.3	293.9	333.6	-	246.4	392.6	297.6	336.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	913	11.8	(3) 4"	730	9.6	(2) 4"	1096	16.5	(3) 4"
EAW-FD1556ZB400B3-632AXSP04	257.40	416.2	314.7	356.3	703.1	264	418.7	318.5	359	700.3	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400C3-425AXSP04	241.30	393.1	295	335.2	-	246.6	394.9	298.2	337.8	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400C3-432AXSP04	224.00	367.5	275	313.1	-	228.9	369.9	278	315.3	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400C3-525AXSP04	264.20	425.1	321	363.5	-	270.3	427.8	324.5	366.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400C3-532AXSP04	249.50	405.2	304.6	346	-	254.9	407.2	308.1	348.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400C3-625AXSP04	279.90	446.5	339.4	382.9	748.8	286.9	449.2	343.3	385.8	746.4	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400C3-632AXSP04	268.30	433.4	327.7	370.7	733.3	274.6	435.8	331.5	373.4	729.9	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400C9-425AXSP04	241.30	393.1	295	335.2	-	246.6	394.9	298.2	337.8	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400C9-432AXSP04	224.00	367.5	275	313.1	-	228.9	369.9	278	315.3	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400C9-525AXSP04	264.20	425.1	321	363.5	-	270.3	427.8	324.5	366.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400C9-532AXSP04	249.50	405.2	304.6	346	-	254.9	407.2	308.1	348.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400C9-625AXSP04	279.90	446.5	339.4	382.9	748.8	286.9	449.2	343.3	385.8	746.4	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400C9-632AXSP04	268.30	433.4	327.7	370.7	733.3	274.6	435.8	331.5	373.4	729.9	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400K3-425AXSP04	234.70	381.4	286.5	325.5	-	239.4	383.8	289.8	327.5	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400K3-432AXSP04	217.60	356.8	266.9	303.9	-	222	358.1	269.6	305.6	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400K3-525AXSP04	258.20	415.4	314	355.4	-	263.8	416.9	316.5	357.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400K3-532AXSP04	242.50	394	296.6	336.7	-	248	396	299.5	338.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400K3-625AXSP04	275.70	439.5	334.3	377.1	736.9	281.7	441.4	337.5	379.2	733.1	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400K3-632AXSP04	262.10	423.6	320.6	362.5	717.1	268.5	425.5	323.4	364.7	712	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400K9-425AXSP04	234.70	381.4	286.5	325.5	-	239.4	383.8	289.8	327.5	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400K9-432AXSP04	217.60	356.8	266.9	303.9	-	222	358.1	269.6	305.6	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400K9-525AXSP04	258.20	415.4	314	355.4	-	263.8	416.9	316.5	357.3	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400K9-532AXSP04	242.50	394	296.6	336.7	-	248	396	299.5	338.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400K9-625AXSP04	275.70	439.5	334.3	377.1	736.9	281.7	441.4	337.5	379.2	733.1	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400K9-632AXSP04	262.10	423.6	320.6	362.5	717.1	268.5	425.5	323.4	364.7	712	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400R3-425AXSP04	237.30	386.1	290.4	329.3	-	242.2	388	293.3	331.5	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400R3-432AXSP04	220.20	360.7	270.1	307.7	-	224.8	363	272.8	309.3	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB400R3-525AXSP04	261.30	420	317.3	359.3	-	266.6	421.8	320.6	361.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400R3-532AXSP04	245.50	398.6	299.9	340.5	-	250.8	400.1	303	342.4	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB400R3-625AXSP04	278.60	444.3	337.8	381.1	745	284.8	446.3	341.2	383.4	741.5	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB400R3-632AXSP04	265.20	428.1	323.9	366.8	725.1	271.3	430.2	327.4	368.7	721.2	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB50B3-425AXSP04	250.40	408.3	306.6	348.3	-	256.5	411.8	310.4	351.3	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB50B3-432AXSP04	233.20	383.3	286.4	326.4	-	238.7	385.6	289.9	328.9	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB50B3-525AXSP04	272.80	439.1	331.6	375.8	-	279.3	443	336.1	379.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB50B3-532AXSP04	258.50	419.8	315.5	358.7	-	264.7	423.3	319.7	361.6	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB50B3-625AXSP02	-	-	-	-	-	-	-	-	-	-	913	11.8	(3) 4"	730	9.6	(2) 4"	1096	16.5	(3) 4"
EAW-FD1556ZB50B3-632AXSP04	-	-	-	-	-	284.2	450.5	342.2	386.2	756.4	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550C2-425AXSP02	-	379.7	261.9	313.4	697.1	208.5	392	278.4	326.4	701.9	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550C2-432AXSP04	246.50	405.8	303	345.6	-	252.1	408.4	306.7	348.1	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550C2-525AXSP04	293.10	473.6	357	404.5	-	300.1	476.7	361.7	407.9	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550C2-532AXSP04	275.60	448.4	336.9	383	-	281.9	451.5	341.1	385.7	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550C2-625AXSP04	312.80	499.7	378.9	428.2	-	320.3	503.4	383.8	432	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550C2-632AXSP04																			

EAW-FD1556ZB550K2-432AXSP04	236.70	388.8	290.8	331.2	-	242.1	391.3	294.1	333.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550K2-525AXSP04	281.90	454.8	343	388.9	-	287.7	456.7	346.5	391.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K2-532AXSP04	264.50	430.4	323.1	367.5	-	270.3	432.7	327	369.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K2-625AXSP04	302.00	481.5	365.6	412.9	-	308.4	483.8	369.3	415.5	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K2-632AXSP04	287.10	463.5	350	396.4	-	293.8	465.7	353.3	399	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K3-425AXSP02	-	362.6	249.8	299.2	667	-	374.3	265.6	311.6	670.5	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550K3-432AXSP04	236.70	388.8	290.8	331.2	-	242.1	391.3	294.1	333.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550K3-525AXSP04	281.90	454.8	343	388.9	-	287.7	456.7	346.5	391.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K3-532AXSP04	264.50	430.4	323.1	367.5	-	270.3	432.7	327	369.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K3-625AXSP04	302.00	481.5	365.6	412.9	-	308.4	483.8	369.3	415.5	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K3-632AXSP04	287.10	463.5	350	396.4	-	293.8	465.7	353.3	399	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K4-425AXSP02	-	362.6	249.8	299.2	667	-	374.3	265.6	311.6	670.5	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550K4-432AXSP04	236.70	388.8	290.8	331.2	-	242.1	391.3	294.1	333.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550K4-525AXSP04	281.90	454.8	343	388.9	-	287.7	456.7	346.5	391.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K4-532AXSP04	264.50	430.4	323.1	367.5	-	270.3	432.7	327	369.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K4-625AXSP04	302.00	481.5	365.6	412.9	-	308.4	483.8	369.3	415.5	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K4-632AXSP04	287.10	463.5	350	396.4	-	293.8	465.7	353.3	399	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K5-425AXSP02	-	362.6	249.8	299.2	667	-	374.3	265.6	311.6	670.5	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550K5-432AXSP04	236.70	388.8	290.8	331.2	-	242.1	391.3	294.1	333.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550K5-525AXSP04	281.90	454.8	343	388.9	-	287.7	456.7	346.5	391.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K5-532AXSP04	264.50	430.4	323.1	367.5	-	270.3	432.7	327	369.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K5-625AXSP04	302.00	481.5	365.6	412.9	-	308.4	483.8	369.3	415.5	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K5-632AXSP04	287.10	463.5	350	396.4	-	293.8	465.7	353.3	399	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K8-425AXSP02	-	362.6	249.8	299.2	667	-	374.3	265.6	311.6	670.5	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550K8-432AXSP04	236.70	388.8	290.8	331.2	-	242.1	391.3	294.1	333.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550K8-525AXSP04	281.90	454.8	343	388.9	-	287.7	456.7	346.5	391.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K8-532AXSP04	264.50	430.4	323.1	367.5	-	270.3	432.7	327	369.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K8-625AXSP04	302.00	481.5	365.6	412.9	-	308.4	483.8	369.3	415.5	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K8-632AXSP04	287.10	463.5	350	396.4	-	293.8	465.7	353.3	399	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K9-425AXSP02	-	362.6	249.8	299.2	667	-	374.3	265.6	311.6	670.5	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550K9-432AXSP04	236.70	388.8	290.8	331.2	-	242.1	391.3	294.1	333.7	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550K9-525AXSP04	281.90	454.8	343	388.9	-	287.7	456.7	346.5	391.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K9-532AXSP04	264.50	430.4	323.1	367.5	-	270.3	432.7	327	369.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550K9-625AXSP04	302.00	481.5	365.6	412.9	-	308.4	483.8	369.3	415.5	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550K9-632AXSP04	287.10	463.5	350	396.4	-	293.8	465.7	353.3	399	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550R3-425AXSP02	-	370	255.1	305.4	680.4	-	381.9	271.1	317.9	684.4	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB550R3-432AXSP04	241.00	396.2	296.4	337.3	-	246.4	398.7	299.5	340.1	-	304	21.3	4"	244	17.1	3"	365	29.9	4"
EAW-FD1556ZB550R3-525AXSP04	286.90	463.6	349.3	396.2	-	293.1	465.7	353.1	398.7	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550R3-532AXSP04	269.30	438.6	329.5	374.3	-	275.5	441.2	333.1	376.5	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB550R3-625AXSP04	307.60	490.1	371.8	420.1	-	314.2	493.4	375.9	423	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB550R3-632AXSP04	292.50	471.9	356.1	403.4	-	299.6	474.7	360.4	406.4	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K2-425AXSP02	-	384.3	265.4	317.4	705.5	211.3	396.9	281.9	330.3	709.3	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K2-432AXSP02	-	355.5	243.4	292.5	659.6	-	367.4	259.5	305.1	664.6	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K2-525AXSP04	296.50	479.4	361.2	409.3	-	303.6	482.7	365.4	412.8	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K2-532AXSP04	278.50	453.5	340.9	387.3	-	285	456.9	344.9	390.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K2-625AXSP04	316.90	505.9	384	434	-	324.3	509.3	388.7	436.9	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K2-632AXSP04	302.30	487.1	367.6	416.7	-	309.1	490.9	372.2	420	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K3-425AXSP02	-	384.3	265.4	317.4	705.5	211.3	396.9	281.9	330.3	709.3	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K3-432AXSP02	-	355.5	243.4	292.5	659.6	-	367.4	259.5	305.1	664.6	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K3-525AXSP04	296.50	479.4	361.2	409.3	-	303.6	482.7	365.4	412.8	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K3-532AXSP04	278.50	453.5	340.9	387.3	-	285	456.9	344.9	390.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K3-625AXSP04	316.90	505.9	384	434	-	324.3	509.3	388.7	436.9	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K3-632AXSP04	302.30	487.1	367.6	416.7	-	309.1	490.9	372.2	420	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K4-425AXSP02	-	384.3	265.4	317.4	705.5	211.3	396.9	281.9	330.3	709.3	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K4-432AXSP02	-	355.5	243.4	292.5	659.6	-	367.4	259.5	305.1	664.6	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K4-525AXSP04	296.50	479.4	361.2	409.3	-	303.6	482.7	365.4	412.8	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K4-532AXSP04	278.50	453.5	340.9	387.3	-	285	456.9	344.9	390.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K4-625AXSP04	316.90	505.9	384	434	-	324.3	509.3	388.7	436.9	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K4-632AXSP04	302.30	487.1	367.6	416.7	-	309.1	490.9	372.2	420	-	456	20.3	(2) 4"	365	15.9	4"	548	28.4	(2) 4"
EAW-FD1556ZB750K5-425AXSP02	-	384.3	265.4	317.4	705.5	211.3	396.9	281.9	330.3	709.3	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K5-432AXSP02	-	355.5	243.4	292.5	659.6	-	367.4	259.5	305.1	664.6	609	11.8	(2) 4"	487	7.7	(2) 4"	730	16.5	(2) 4"
EAW-FD1556ZB750K5-525AXSP04	296.50	479.4	361.2	409.3	-	303.6	482.7	365.4	412.8	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K5-532AXSP04	278.50	453.5	340.9	387.3	-	285	456.9	344.9	390.1	-	378	22.5	4"	302	14.8	4"	453	27.8	(2) 4"
EAW-FD1556ZB750K5-625AXSP04	316.90	505.9	384	434	-	324.3	509.3	388.7	436.9	-	456	20.3							

Note: "-" indicates flow rate is outside of unit capability

EAW-FD1556ZK370C8-425AXSP02	-	376	264.3	312.8	679.4	212.3	385.1	277.3	322.7	679.8	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK370C8-432AXSP04	244.50	396.9	298.4	338.7	-	248.6	398.3	300.3	339.8	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370C8-525AXSP04	289.80	461.9	350.3	395.6	-	294.5	463	352.6	397.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370C8-532AXSP04	273.30	438.9	331.5	375.4	-	277.8	440.3	334.1	376.5	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370C8-625AXSP04	309.20	487	371.5	418.2	-	314.4	488.1	374.2	419.7	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370C8-632AXSP04	296.20	470.9	357.5	403.9	-	301.1	471.7	360.1	405.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K2-425AXSP04	255.20	411.3	310.1	351.7	-	259.2	412.2	312.2	352.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K2-432AXSP04	236.70	383.8	288.5	327.6	-	240.5	384.6	290.3	328.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K2-525AXSP04	281.50	447.9	340	383.8	-	286	448.9	342.2	384.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K2-532AXSP04	264.70	424.9	321.4	363.7	-	269	425.4	323.3	364.8	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K2-625AXSP04	302.20	474.8	362.4	408.4	-	306.5	475.2	364.6	408.8	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K2-632AXSP04	287.50	457.1	347.4	392.4	-	292.2	457.8	349.4	393	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K4-425AXSP04	255.20	411.3	310.1	351.7	-	259.2	412.2	312.2	352.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K4-432AXSP04	236.70	383.8	288.5	327.6	-	240.5	384.6	290.3	328.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K4-525AXSP04	281.50	447.9	340	383.8	-	286	448.9	342.2	384.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K4-532AXSP04	264.70	424.9	321.4	363.7	-	269	425.4	323.3	364.8	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K4-625AXSP04	302.20	474.8	362.4	408.4	-	306.5	475.2	364.6	408.8	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K4-632AXSP04	287.50	457.1	347.4	392.4	-	292.2	457.8	349.4	393	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K5-425AXSP04	255.20	411.3	310.1	351.7	-	259.2	412.2	312.2	352.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K5-432AXSP04	236.70	383.8	288.5	327.6	-	240.5	384.6	290.3	328.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K5-525AXSP04	281.50	447.9	340	383.8	-	286	448.9	342.2	384.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K5-532AXSP04	264.70	424.9	321.4	363.7	-	269	425.4	323.3	364.8	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K5-625AXSP04	302.20	474.8	362.4	408.4	-	306.5	475.2	364.6	408.8	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K5-632AXSP04	287.50	457.1	347.4	392.4	-	292.2	457.8	349.4	393	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K8-425AXSP04	255.20	411.3	310.1	351.7	-	259.2	412.2	312.2	352.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K8-432AXSP04	236.70	383.8	288.5	327.6	-	240.5	384.6	290.3	328.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK370K8-525AXSP04	281.50	447.9	340	383.8	-	286	448.9	342.2	384.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K8-532AXSP04	264.70	424.9	321.4	363.7	-	269	425.4	323.3	364.8	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK370K8-625AXSP04	302.20	474.8	362.4	408.4	-	306.5	475.2	364.6	408.8	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK370K8-632AXSP04	287.50	457.1	347.4	392.4	-	292.2	457.8	349.4	393	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400B3-425AXSP04	255.20	410.8	310.3	351.2	-	259.4	411.9	312.5	352.7	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400B3-432AXSP04	237.50	385.3	289.5	328.8	-	241.3	386.5	291.6	329.9	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400B3-525AXSP04	279.20	444	337.2	380.6	-	284.3	445.4	339.6	382.3	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400B3-532AXSP04	264.20	423.9	320.1	362.9	-	268.5	425.3	322.6	364.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400B3-625AXSP04	296.30	466.5	358.8	400.9	-	301.9	467.9	359.1	402.6	-	456	22.3	(2) 4"	365	17.2	4"	548	30.6	(2) 4"
EAW-FD1556ZK400B3-632AXSP04	284.90	453.4	344.2	388.7	761.4	290.3	454.5	347	390.2	757	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400C3-425AXSP02	-	376	264.3	312.8	679.4	212.3	385.1	277.3	322.7	679.8	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK400C3-432AXSP04	244.50	396.9	298.4	338.7	-	248.6	398.3	300.3	339.8	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400C3-525AXSP04	289.80	461.9	350.3	395.6	-	294.5	463	352.6	397.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400C3-532AXSP04	273.30	438.9	331.5	375.4	-	277.8	440.3	334.1	376.5	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400C3-625AXSP04	309.20	487	371.5	418.2	-	314.4	488.1	374.2	419.7	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400C3-632AXSP04	296.20	470.9	357.5	403.9	-	301.1	471.7	360.1	405.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400C9-425AXSP02	-	376	264.3	312.8	679.4	212.3	385.1	277.3	322.7	679.8	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK400C9-432AXSP04	244.50	396.9	298.4	338.7	-	248.6	398.3	300.3	339.8	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400C9-525AXSP04	289.80	461.9	350.3	395.6	-	294.5	463	352.6	397.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400C9-532AXSP04	273.30	438.9	331.5	375.4	-	277.8	440.3	334.1	376.5	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400C9-625AXSP04	309.20	487	371.5	418.2	-	314.4	488.1	374.2	419.7	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400C9-632AXSP04	296.20	470.9	357.5	403.9	-	301.1	471.7	360.1	405.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400K3-425AXSP04	255.20	411.3	310.1	351.7	-	259.2	412.2	312.2	352.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400K3-432AXSP04	236.70	383.8	288.5	327.6	-	240.5	384.6	290.3	328.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400K3-525AXSP04	281.50	447.9	340	383.8	-	286	448.9	342.2	384.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400K3-632AXSP04	264.70	424.9	321.4	363.7	-	269	425.4	323.3	364.8	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400K3-625AXSP04	302.20	474.8	362.4	408.4	-	306.5	475.2	364.6	408.8	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400K3-632AXSP04	287.50	457.1	347.4	392.4	-	292.2	457.8	349.4	393	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400K9-425AXSP04	255.20	411.3	310.1	351.7	-	259.2	412.2	312.2	352.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400K9-432AXSP04	236.70	383.8	288.5	327.6	-	240.5	384.6	290.3	328.4	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400K9-525AXSP04	281.50	447.9	340	383.8	-	286	448.9	342.2	384.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400K9-532AXSP04	264.70	424.9	321.4	363.7	-	269	425.4	323.3	364.8	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400K9-625AXSP04	302.20	474.8	362.4	408.4	-	306.5	475.2	364.6	408.8	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400K9-632AXSP04	287.50	457.1	347.4	392.4	-	292.2	457.8	349.4	393	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK400R3-425AXSP02	-	368.3	258.6	306.2	665.6	208	377.5	271.4	315.9	666.7	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK400R3-432AXSP04	239.70	388.9	292.3	332.1	-	243.7	389.8	294.3	333.2	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK400R3-525AXSP04	284.90	453.6	344.2	388.6	-	289.6	454.1	346.6	389.7	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK400R3-532AXSP04	268.																		

EAW-FD1556ZK550C8-632AXSP04	328.90	524.7	397.9	449.7	-	334.6	526.6	400.9	451.9	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550C9-425AXSP02	214.00	419	296.2	349.4	756	238.1	428.5	309.8	360.1	758	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550C9-432AXSP02	-	387.6	271.4	321.7	705.4	217.1	397.5	284.7	332.2	707.9	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550C9-525AXSP02	-	458.4	323.6	382.3	822	261.6	470.4	339.7	394.6	824.6	761	14	(2) 4"	609	9.2	(2) 4"	913	16.9	(3) 4"
EAW-FD1556ZK550C9-532AXSP04	302.30	487.4	367.5	416.3	-	307.8	488.8	370.3	418.2	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550C9-625AXSP04	345.40	545.7	415.9	468.9	-	351.6	547.8	419	470.6	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550C9-632AXSP04	328.90	524.7	397.9	449.7	-	334.6	526.6	400.9	451.9	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K2-632AXSP02	-	400.6	282.1	333.4	721.6	226.9	409.9	295.5	343.4	724	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K2-432AXSP02	-	370.4	259.1	307.2	674.8	207.1	379.8	272	317.2	676.6	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K2-525AXSP04	308.60	492.3	372.9	421.6	-	313.8	493.6	376.1	423.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K2-532AXSP04	289.50	466	351.6	398.6	-	294.5	467.8	354.6	400.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K2-625AXSP04	331.30	522.9	398.6	449.1	-	336.8	523.6	401.1	450.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K2-632AXSP04	315.10	502.1	380.8	430.1	-	320.6	503.1	383.8	431.5	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K3-425AXSP02	-	400.6	282.1	333.4	721.6	226.9	409.9	295.5	343.4	724	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K3-432AXSP02	-	370.4	259.1	307.2	674.8	207.1	379.8	272	317.2	676.6	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K3-525AXSP04	308.60	492.3	372.9	421.6	-	313.8	493.6	376.1	423.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K3-532AXSP04	289.50	466	351.6	398.6	-	294.5	467.8	354.6	400.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K3-625AXSP04	331.30	522.9	398.6	449.1	-	336.8	523.6	401.1	450.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K3-632AXSP04	315.10	502.1	380.8	430.1	-	320.6	503.1	383.8	431.5	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K4-425AXSP02	-	400.6	282.1	333.4	721.6	226.9	409.9	295.5	343.4	724	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K4-432AXSP02	-	370.4	259.1	307.2	674.8	207.1	379.8	272	317.2	676.6	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K4-525AXSP04	308.60	492.3	372.9	421.6	-	313.8	493.6	376.1	423.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K4-532AXSP04	289.50	466	351.6	398.6	-	294.5	467.8	354.6	400.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K4-625AXSP04	331.30	522.9	398.6	449.1	-	336.8	523.6	401.1	450.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K4-632AXSP04	315.10	502.1	380.8	430.1	-	320.6	503.1	383.8	431.5	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K5-425AXSP02	-	400.6	282.1	333.4	721.6	226.9	409.9	295.5	343.4	724	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K5-432AXSP02	-	370.4	259.1	307.2	674.8	207.1	379.8	272	317.2	676.6	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K5-525AXSP04	308.60	492.3	372.9	421.6	-	313.8	493.6	376.1	423.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K5-532AXSP04	289.50	466	351.6	398.6	-	294.5	467.8	354.6	400.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K5-625AXSP04	331.30	522.9	398.6	449.1	-	336.8	523.6	401.1	450.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K5-632AXSP04	315.10	502.1	380.8	430.1	-	320.6	503.1	383.8	431.5	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K8-425AXSP02	-	400.6	282.1	333.4	721.6	226.9	409.9	295.5	343.4	724	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K8-432AXSP02	-	370.4	259.1	307.2	674.8	207.1	379.8	272	317.2	676.6	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K8-525AXSP04	308.60	492.3	372.9	421.6	-	313.8	493.6	376.1	423.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K8-532AXSP04	289.50	466	351.6	398.6	-	294.5	467.8	354.6	400.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K8-625AXSP04	331.30	522.9	398.6	449.1	-	336.8	523.6	401.1	450.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K8-632AXSP04	315.10	502.1	380.8	430.1	-	320.6	503.1	383.8	431.5	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K9-425AXSP02	-	400.6	282.1	333.4	721.6	226.9	409.9	295.5	343.4	724	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K9-432AXSP02	-	370.4	259.1	307.2	674.8	207.1	379.8	272	317.2	676.6	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550K9-525AXSP04	308.60	492.3	372.9	421.6	-	313.8	493.6	376.1	423.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K9-532AXSP04	289.50	466	351.6	398.6	-	294.5	467.8	354.6	400.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550K9-625AXSP04	331.30	522.9	398.6	449.1	-	336.8	523.6	401.1	450.2	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550K9-632AXSP04	315.10	502.1	380.8	430.1	-	320.6	503.1	383.8	431.5	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550R3-425AXSP02	207.80	408.7	288.2	340.5	737.4	231.9	418.7	301.7	350.8	739.3	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550R3-432AXSP02	-	378.3	264.8	313.9	689.8	212	388.2	277.9	324	690.8	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK550R3-525AXSP04	314.70	502.5	380.3	430.2	-	319.6	504.2	383.2	432.2	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550R3-532AXSP04	295.10	475.6	358.5	406.6	-	300.4	476.9	361.8	408.4	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK550R3-625AXSP04	337.70	533.6	406.4	458	-	343.4	534.5	409.2	459.4	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK550R3-632AXSP04	321.10	512.3	388.2	438.6	-	326.9	513.6	391.4	440.3	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK750C4-425AXSP04	304.60	493.6	371.4	421.4	-	310.1	495.7	374.8	423.6	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK750C4-432AXSP04	281.60	459.4	344.5	391.8	-	286.8	461.5	347.6	393.9	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK750C4-525AXSP04	335.00	536.4	405.5	459.2	-	341.5	539.1	409.9	462.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK750C4-532AXSP04	314.80	508.2	383.1	434.4	-	320.6	510.9	386.2	436.6	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK750C4-632AXSP04	341.40	545.1	413.4	467.5	-	347.6	548.2	416.7	470.1	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK750C5-425AXSP04	304.60	493.6	371.4	421.4	-	310.1	495.7	374.8	423.6	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK750C5-432AXSP04	281.60	459.4	344.5	391.8	-	286.8	461.5	347.6	393.9	-	304	23.3	4"	244	18.4	3"	365	32.7	4"
EAW-FD1556ZK750C5-525AXSP04	335.00	536.4	405.5	459.2	-	341.5	539.1	409.9	462.1	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK750C5-532AXSP04	314.80	508.2	383.1	434.4	-	320.6	510.9	386.2	436.6	-	378	24.5	4"	302	16.1	4"	453	30.6	(2) 4"
EAW-FD1556ZK750C5-632AXSP04	341.40	545.1	413.4	467.5	-	347.6	548.2	416.7	470.1	-	456	22.3	(2) 4"	365	17.2	4"	548	31.2	(2) 4"
EAW-FD1556ZK750K2-425AXSP02	217.50	424.6	300.5	354.7	766.4	241.8	435.3	314.4	365.6	769.4	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK750K2-432AXSP02	-	394.2	276.3	327.3	717.6	221.1	404.2	289.8	338	719.4	609	12.8	(2) 4"	487	8.4	(2) 4"	730	17.9	(2) 4"
EAW-FD1556ZK750K2-525AXSP02	-	464.7	327.9	386.7	832.6	265	476.2	344.3	400	835.4	761	14	(2) 4"	609	9.2	(2) 4"	913	16.9	(3) 4"
EAW-FD1556ZK750K2-532AXSP04</																			

EAW-FD91S1WK177F7-425AXSP16	21.00	36.6	26.9	31	63.2	22	36.8	27.4	31.2	62.6	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK177F7-432AXSP16	19.20	34	24.9	28.7	59.3	20.3	34.2	25.3	29	58.8	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK177F7-535AXSP16	22.70	39.4	29	33.4	67.5	23.9	39.6	29.6	33.6	66.8	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK177F7-532AXSP16	-	37	27.1	31.3	64.2	-	37.3	27.7	31.6	63.6	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK177F7-625AXSP16	-	42.6	31.5	36.1	72.3	-	42.8	32.1	36.4	71.4	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK177F7-632AXSP16	-	40.6	29.9	34.4	69.8	-	40.9	30.5	34.8	69.1	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK24716-425AXSP16	23.20	40.2	29.6	34	69.5	24.2	40.4	30.1	34.3	68.8	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK24716-432AXSP16	21.20	37.3	27.2	31.5	64.9	22.3	37.5	27.7	31.7	64.4	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK24716-525AXSP16	25.10	43.4	32	36.8	74.4	26.4	43.6	32.6	37.1	73.6	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK24716-532AXSP16	23.20	40.7	29.8	34.4	70.5	24.4	40.9	30.4	34.8	69.9	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK24716-625AXSP16	-	47	34.8	39.9	79.9	28.8	47.3	35.5	40.3	79	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK24716-632AXSP16	-	44.8	32.9	38	77	-	45.1	33.7	38.4	76.3	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK320P5-425AXSP16	25.40	43.6	32.3	37.2	75.7	26.5	43.9	32.8	37.4	75	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK320P5-432AXSP16	23.10	40.3	29.6	34.2	70.4	24.1	40.6	30.1	34.4	69.8	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK320P5-525AXSP16	27.70	47.6	35.2	40.4	81.7	28.9	47.8	35.7	40.7	80.9	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK320P5-532AXSP16	25.40	44.5	32.6	37.6	77	26.7	44.7	33.2	37.9	76.3	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK320P5-625AXSP16	30.50	52.2	38.7	44.3	88.6	31.9	52.3	39.3	44.6	87.6	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK320P5-632AXSP16	28.30	49.3	36.3	41.8	84.7	29.8	49.6	37	42.1	83.8	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK320P7-425AXSP16	25.90	44.6	33	37.9	77.3	27	44.8	33.5	38.2	76.7	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK320P7-432AXSP16	23.60	41.2	30.2	34.9	71.9	24.7	41.4	30.7	35.2	71.4	56	21.1	1-1/2"	45	13.9	1-1/2"	68	29.6	1-1/2"
EAW-FD91S1WK320P7-525AXSP16	28.30	48.6	35.9	41.3	83.5	29.6	48.8	36.5	41.6	82.7	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK320P7-532AXSP16	26.00	45.4	33.3	38.4	78.7	27.3	45.6	33.9	38.7	78	68	22.6	1-1/2"	54	14.9	1-1/2"	81	27.2	2"
EAW-FD91S1WK320P7-625AXSP16	31.10	53.3	39.5	45.3	90.5	32.7	53.5	40.1	45.6	89.5	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S1WK320P7-632AXSP16	29.00	50.4	37.1	42.7	86.6	30.5	50.6	37.8	43.1	85.8	84	20.4	2"	68	16.7	1-1/2"	101	28.6	2"
EAW-FD91S2WK177F7-425AXSP12	47.30	75.5	57.3	64.7	-	47.9	75.2	57.3	64.5	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK177F7-432AXSP12	43.60	70.3	53.1	60.1	119.5	44.1	70	53.1	59.9	118.1	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK177F7-525AXSP12	52.10	82.5	63	70.9	137.8	52.8	82.1	63	70.7	135.9	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK177F7-532AXSP12	48.60	78	59.2	66.9	131.1	49.3	77.6	59.2	66.6	129.4	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK177F7-625AXSP16	60.00	91.4	70.7	79	-	60	90.5	70.3	78.2	-	84	33.6	2"	68	25.5	1-1/2"	101	47.2	2"
EAW-FD91S2WK177F7-632AXSP16	57.00	87.7	67.5	75.6	-	57	86.8	67.1	74.9	-	84	33.6	2"	68	25.5	1-1/2"	101	47.2	2"
EAW-FD91S2WK24716-425AXSP12	51.70	82.7	62.6	70.8	-	52.3	82.4	62.6	70.6	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK24716-432AXSP12	47.60	76.8	57.9	65.6	-	48.2	76.5	58	65.5	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK24716-525AXSP12	57.30	90.7	69.1	77.8	-	57.9	90.4	69.1	77.6	149.9	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK24716-532AXSP12	53.30	85.4	64.8	73.2	144	54	85	64.8	73	142.3	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK24716-625AXSP12	62.80	98.6	75.7	84.9	162.8	63.5	98	75.6	84.6	160.6	113	28	2"	90	18.5	2"	135	33.8	3"
EAW-FD91S2WK24716-632AXSP16	62.40	96.3	74.2	83	-	62.5	95.6	73.7	82.4	-	84	33.6	2"	68	25.5	1-1/2"	101	47.2	2"
EAW-FD91S2WK320P5-425AXSP12	56.00	89.9	67.9	76.9	-	56.7	89.6	68	76.7	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK320P5-432AXSP12	51.40	83	62.5	70.9	-	52	82.7	62.6	70.8	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK320P5-525AXSP12	62.70	99.4	75.6	85.3	-	63.3	99	75.6	85	-	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK320P5-532AXSP12	58.10	93	70.4	79.6	-	58.7	92.6	70.4	79.3	-	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK320P5-625AXSP12	69.50	109	83.5	93.8	180.8	70.2	108.4	83.4	93.4	178.2	113	28	2"	90	18.5	2"	135	33.8	3"
EAW-FD91S2WK320P5-632AXSP12	65.10	103.5	78.8	88.8	172.9	65.8	102.9	78.8	88.5	170.6	113	28	2"	90	18.5	2"	135	33.8	3"
EAW-FD91S2WK320P7-425AXSP12	57.30	91.8	69.4	78.5	-	57.8	91.4	69.4	78.3	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK320P7-432AXSP12	52.40	84.7	63.8	72.4	-	53	84.5	63.9	72.3	-	73	25.2	2"	59	19.1	1-1/2"	88	35.4	2"
EAW-FD91S2WK320P7-525AXSP12	64.00	101.5	77.1	87.1	-	64.6	101.1	77.1	86.8	-	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK320P7-532AXSP12	59.30	94.8	71.9	81.2	-	60	94.6	71.9	81	-	90	26.3	2"	72	17.3	2"	108	36.9	2"
EAW-FD91S2WK320P7-625AXSP12	70.90	111.3	85.1	95.7	184.7	71.7	110.7	85.1	95.3	182.1	113	28	2"	90	18.5	2"	135	33.8	3"
EAW-FD91S2WK320P7-632AXSP12	66.50	105.6	80.5	90.6	176.6	67.3	105.2	80.4	90.3	174.4	113	28	2"	90	18.5	2"	135	33.8	3"
EAW-FD91S3WK177F7-425AXSP08	71.80	114.5	86.9	98.2	-	72.6	114.1	86.9	97.9	-	113	26.9	2"	90	17.7	2"	135	32.2	3"
EAW-FD91S3WK177F7-432AXSP08	66.10	106.7	80.7	91.3	181.1	66.9	106.3	80.7	91.1	178.9	113	26.9	2"	90	17.7	2"	135	32.2	3"
EAW-FD91S3WK177F7-525AXSP08	79.50	126	96.2	108.2	209.8	80.6	125.3	96.2	107.8	206.9	141	23.5	3"	113	19.5	2"	169	33	3"
EAW-FD91S3WK177F7-532AXSP08	74.30	119.2	90.5	102.2	200	75.4	118.6	90.5	101.9	197.4	141	23.5	3"	113	19.5	2"	169	33	3"
EAW-FD91S3WK177F7-625AXSP08	85.20	133.9	102.6	115.4	220.6	86.3	133.1	102.6	114.9	217.2	169	24.2	3"	135	16	3"	203	33.9	3"
EAW-FD91S3WK177F7-632AXSP08	80.60	128.3	97.7	110.3	213.1	81.7	127.6	97.8	109.9	210.3	169	24.2	3"	135	16	3"	203	33.9	3"
EAW-FD91S3WK24716-425AXSP08	78.50	125.4	95	107.5	-	79.4	124.9	95.1	107.1	-	113	26.9	2"	90	17.7	2"	135	32.2	3"
EAW-FD91S3WK24716-432AXSP08	72.30	116.6	87.9	99.7	-	73.2	116.2	88.2	99.5	-	113	26.9	2"	90	17.7	2"	135	32.2	3"
EAW-FD91S3WK24716-525AXSP08	87.60	138.6	105.6	119	231.4	88.5	137.8	105.6	118.5	228.5	141	23.5	3"	113	19.5	2"	169	33	3"
EAW-FD91S3WK24716-532AXSP08	81.50	130.7	99.2	112	220.1	82.7	130	99.3	111.6	217.1	141	23.5	3"	113	19.5	2"	169	33	3"
EAW-FD91S3WK24716-625AXSP08	93.90	147.6	113.2	127	243.6	95	146.8	113.1	126.6	240.4	169	24.2	3"	135	16	3"	203	33.9	3"
EAW-FD91S3WK24716-632AXSP08	88.60	141.1	107.5	121.3	235.1	89.9	140.4	107.6	120.9	232.2	169	24.2	3"	135	16	3"	203	33.9	3"
EAW-FD91S3WK320P5-425AXSP08	85.20	136.4	103.2	116.7	-	86.1	135.9	103.3	116.5	-	113	26.9	2"	90	17.7	2"	135	32.2	3"
EAW-FD91S3WK320P5-432AXSP08	78.10	126.1	95.1	107.8	-	79	125.6	95.2	107.5	-	113	26.9	2"	90	17.7	2"	135	32.2	3"
EAW-FD91S3WK320P5-525AXSP08	96.00	151.9	115.5	130.4	-	96.8	151.2	115.7	130	-	141	23.5	3"	113	19.5	2"	169	33	3"
EAW-FD91S3WK320P5-532AXSP08	89.00	142.4	107.9	121.9	-	90	141.7	108	121.6	-	141	23.5	3"	113	19.5	2"	169	33	3"
EAW-FD91S3WK320P5-625AXSP08	104.00	163.1	124.9	140.4	270.5	105	162.2	124.8	139.8	266.6	169	24.2	3"	135	16	3"	203	33.9	3

EAW-FD915SWK177F7-632AXSP06	139.90	217	166.8	187	357.8	140.5	215.2	166	185.6	352.2	225	30.2	3"	180	19.9	3"	270	38.9	4"
EAW-FD915SWK24716-425AXSP04	123.80	203.4	153.1	173.8	347.8	126.5	203.4	153.9	174.1	344.3	225	21.4	3"	180	14.1	3"	270	26.5	4"
EAW-FD915SWK24716-432AXSP04	113.40	189	141.2	161	325.1	116.4	189.1	142.3	161.4	322.1	225	21.4	3"	180	14.1	3"	270	26.5	4"
EAW-FD915SWK24716-525AXSP06	149.80	233.2	178.7	200.6	-	150.4	231.2	178	199.2	-	186	29	3"	149	19.2	3"	223	40.8	3"
EAW-FD915SWK24716-532AXSP06	139.90	219.7	167.7	188.7	-	140.6	218.3	167	187.4	-	186	29	3"	149	19.2	3"	223	40.8	3"
EAW-FD915SWK24716-625AXSP06	162.20	249.3	192.3	215.1	-	162.8	247.5	191.4	213.7	-	225	30.2	3"	180	19.9	3"	270	38.9	4"
EAW-FD915SWK24716-632AXSP06	153.70	238.6	183	205.3	-	154.3	236.8	182.5	204	-	225	30.2	3"	180	19.9	3"	270	38.9	4"
EAW-FD915SWK320P5-425AXSP04	135.00	221.2	166.4	188.8	-	137.8	221.2	167.3	189.2	375.1	225	21.4	3"	180	14.1	3"	270	26.5	4"
EAW-FD915SWK320P5-432AXSP04	123.10	204.2	153	174.2	352.2	126	204.3	154	174.6	348.8	225	21.4	3"	180	14.1	3"	270	26.5	4"
EAW-FD915SWK320P5-525AXSP04	151.40	246.7	186.5	211	417.8	154.7	246.4	187.4	211.2	413	282	19.5	4"	225	15.4	3"	338	27.4	4"
EAW-FD915SWK320P5-532AXSP04	139.70	231.1	173.3	197.2	394.4	143.1	230.8	174.3	197.4	389.5	282	19.5	4"	225	15.4	3"	338	27.4	4"
EAW-FD915SWK320P5-625AXSP06	178.70	275.7	212.3	237.8	-	179.3	273.4	211.2	236.1	-	225	30.2	3"	180	19.9	3"	270	38.9	4"
EAW-FD915SWK320P5-632AXSP06	168.10	261.5	200.6	225.3	-	168.4	259.4	199.6	223.4	-	225	30.2	3"	180	19.9	3"	270	38.9	4"
EAW-FD915SWK320P7-425AXSP04	137.80	225.8	169.7	192.7	-	140.8	225.9	170.7	193.1	-	225	21.4	3"	180	14.1	3"	270	26.5	4"
EAW-FD915SWK320P7-432AXSP04	125.70	208.6	156.1	177.8	360.1	128.6	208.7	157.1	178.3	356.3	225	21.4	3"	180	14.1	3"	270	26.5	4"
EAW-FD915SWK320P7-525AXSP04	154.60	251.8	190.2	215.7	426.8	157.9	251.7	191.3	215.6	422.2	282	19.5	4"	225	15.4	3"	338	27.4	4"
EAW-FD915SWK320P7-532AXSP04	142.70	235.6	177.1	201.3	402.5	146	235.8	178.2	201.5	398.2	282	19.5	4"	225	15.4	3"	338	27.4	4"
EAW-FD915SWK320P7-625AXSP04	167.00	270.7	205.2	232.3	454	171	270.5	206.2	232.5	448.3	338	20.4	4"	270	13.4	4"	406	28.6	4"
EAW-FD915SWK320P7-632AXSP06	171.40	267	204.6	229.9	-	171.9	265	203.8	228.1	-	225	30.2	3"	180	19.9	3"	270	38.9	4"
EAW-FD915SWK177F7-425AXSP04	142.00	227.2	172.1	194.5	-	143.6	226.2	172.3	194.2	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK177F7-432AXSP04	130.70	211.3	159.8	181	359.5	132.5	210.6	160	180.4	355.2	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK177F7-525AXSP04	157.60	250	190.9	214.9	417.1	159.5	249.1	190.9	214.1	411.2	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK177F7-532AXSP04	147.10	236.4	179.3	202.9	397.3	149.2	235.4	179.6	202.1	392.3	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK177F7-625AXSP04	168.90	266.2	203.6	229.4	438.8	171.1	264.6	203.6	228.3	432.5	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK177F7-632AXSP04	159.50	255	193.7	218.8	424.2	162	253.6	193.9	218.2	418.1	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK24716-425AXSP04	155.50	248.8	188.4	212.8	-	157.2	247.9	188.5	212.4	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK24716-432AXSP04	143.00	230.8	174.2	197.6	-	145	230.4	174.7	197.2	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK24716-525AXSP04	173.30	274.9	209.3	235.9	459.8	175.4	273.8	209.6	235.3	454.2	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK24716-532AXSP04	161.30	259	196.4	222.1	436.7	163.7	258.2	196.6	221.5	431.4	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK24716-625AXSP04	186.20	292.9	224.5	252.4	484.9	188.5	291.5	224.8	251.5	478.5	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK24716-632AXSP04	175.50	280.2	213.1	240.4	467.4	178.1	279	213.3	239.7	461.6	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK320P5-425AXSP04	168.40	270.7	204.5	231.4	-	170.4	269.7	204.7	230.9	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK320P5-432AXSP04	154.60	250	188.2	213.6	-	156.4	249	188.5	213.1	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK320P5-525AXSP04	190.20	301.2	229.3	258.4	-	192.1	299.8	229.2	257.6	-	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK320P5-532AXSP04	176.00	282.1	213.5	241.5	-	178	281.2	213.8	241.2	-	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK320P5-625AXSP04	205.80	324.1	247.7	278.8	537.8	208.3	322.3	247.6	277.7	530.7	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK320P5-632AXSP04	192.90	306.9	233.8	263.6	514	195	305.4	233.9	262.7	507.3	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK320P7-425AXSP04	172.10	276	208.7	236.2	-	173.8	275.1	208.9	235.8	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK320P7-432AXSP04	157.70	254.9	192	218	-	159.6	254.5	192.4	217.7	-	225	24.7	3"	180	16.3	3"	270	31.1	4"
EAW-FD915SWK320P7-525AXSP04	194.00	307.5	233.9	264.1	-	196.1	306.3	234	263.1	-	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK320P7-532AXSP04	179.80	288.1	218.2	246.5	-	182	286.9	218.3	245.8	-	282	22.9	4"	225	17.6	3"	338	32.1	4"
EAW-FD915SWK320P7-625AXSP04	210.30	330.3	252.8	284.2	549.4	212.6	328.8	252.8	283.2	541.8	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-FD915SWK320P7-632AXSP04	196.60	313.3	238.5	269	525.7	199.3	312	238.8	268.3	518.5	338	23.7	4"	270	15.6	4"	406	33.3	4"
EAW-HD4053QY037M4-525AXSP02	-	1711.5	1215.2	1428.5	3054.5	-	1744	1266.9	1466.6	3038.2	3156	14.1	6"	2525	9.3	6"	3787	19.8	6"
EAW-HD4053QY037M4-625AXSP02	-	1826.3	1298.4	1527.4	3243.4	-	1864.6	1358.9	1570.5	3229.9	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY037M4-632AXSP02	-	1724.1	-	1437.7	3102.5	-	1764.4	1277.6	1480.4	3089.1	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY037K4-525AXSP02	-	1654.6	1172.4	1382.3	2952.8	-	1688.1	1226.2	1418.5	2940.7	3156	14.1	6"	2525	9.3	6"	3787	19.8	6"
EAW-HD4053QY037K4-625AXSP02	-	1763.3	-	1473.5	3135.4	-	1799.7	1313.3	1516.9	3121.9	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY037K4-632AXSP02	-	1667.5	-	1389.3	3004.3	-	1705.7	-	1432.4	2990.7	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY045M4-525AXSP02	-	1795.2	1276.1	1499	3197.4	-	1827.6	1329.2	1537.5	3186.1	3156	14.1	6"	2525	9.3	6"	3787	19.8	6"
EAW-HD4053QY045M4-625AXSP02	-	1921.5	1367.9	1607.9	3409.7	-	1959.7	1430	1651.4	3395.6	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY045M4-632AXSP02	-	1810.4	1277.1	1507.9	3250.9	-	1848.1	1339.7	1553.9	3238.1	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY045K4-525AXSP02	-	1733.4	1232	1448.7	3091.5	-	1766.9	1284.9	1485.2	3080	3156	14.1	6"	2525	9.3	6"	3787	19.8	6"
EAW-HD4053QY045K4-625AXSP02	-	1852.7	1316.4	1549.1	3287.6	-	1892	1378.2	1593.2	3274.4	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY045K4-632AXSP02	-	1748.7	-	1457.8	3144.1	-	1787.2	1295.5	1501.6	3131.1	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY055M4-525AXSP02	-	1924.1	1368.4	1606.4	3423.3	1105.6	1958.2	1424.4	1647.1	3409.1	3156	14.1	6"	2525	9.3	6"	3787	19.8	6"
EAW-HD4053QY055M4-625AXSP02	-	2061.4	1467.9	1725	3648.2	-	2099	1532	1768.7	3637	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY055M4-632AXSP02	-	1938.6	1370.6	1617.2	3477.9	-	1978.4	1434.3	1663.2	3467.1	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY055K4-525AXSP02	-	1835.7	1306.2	1534.5	3273.7	1055	1870.4	1361.1	1572.4	3259.4	3156	14.1	6"	2525	9.3	6"	3787	19.8	6"
EAW-HD4053QY055K4-625AXSP02	-	1962.9	1398.3	1641.6	3481.5	-	2003.8	1460.9	1687.8	3470.2	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-HD4053QY055K4-632AXSP02	-	1853.6	1308.4	1545.6	3327.1	-	1893.6	1371.2	1588.5	3315.9	3787	15.4	6"	3030	10.1	6"	4544	17	(2) 6"
EAW-VD1551PB370C2-425AXSP16	44.60	79.6	57.9	67.1	139.1	47.4	80.4	59.4	68.1	138.4	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB370C2-432AXSP16	40.70	74	53.5	62.2	130.5	43.4	74.8	54.9	63.1	129.7	113								



EAW-VD1551PB370K5-625AXSP16	-	88.2	64.5	74.6	151.9	-	89.3	66.5	75.8	150.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB370K5-632AXSP16	-	84.5	61.4	71.2	147.4	-	85.7	63.3	72.5	146.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB370K8-425AXSP16	42.80	76.6	55.7	64.6	133.8	45.5	77.3	57	65.5	133.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB370K8-432AXSP16	39.10	71.2	51.4	59.8	125.5	41.8	72.1	52.8	60.8	125	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB370K8-525AXSP16	45.80	81.9	59.7	69.1	142.2	49	82.8	61.3	70.2	141.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB370K8-532AXSP16	-	77.3	56	65	135.5	45.6	78.3	57.6	66.2	134.8	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB370K8-625AXSP16	-	88.2	64.5	74.6	151.9	-	89.3	66.5	75.8	150.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB370K8-632AXSP16	-	84.5	61.4	71.2	147.4	-	85.7	63.3	72.5	146.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K3-425AXSP16	43.20	77.2	56.2	65.2	135.1	45.9	78.1	57.6	66.1	134.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K3-432AXSP16	39.50	72.1	52	60.5	127.1	42.3	72.8	53.5	61.6	126.4	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K3-525AXSP16	46.10	82.5	60.1	69.6	143.2	49.3	83.5	61.8	70.7	142.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K3-532AXSP16	-	78	56.4	65.6	136.8	46.1	79	58.2	66.8	136.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K3-625AXSP16	-	88.4	64.7	74.7	152.3	-	89.6	66.7	76.1	151.5	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K3-632AXSP16	-	85.1	61.8	71.7	148.2	-	86.2	63.8	73.1	147.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400C3-425AXSP16	44.60	79.6	57.9	67.1	139.1	47.4	80.4	59.4	68.1	138.4	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400C3-432AXSP16	40.70	74	53.5	62.2	130.5	43.4	74.8	54.9	63.1	129.7	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400C3-525AXSP16	47.80	85.4	62.3	72	148.2	51	86.3	63.9	73.2	147.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400C3-532AXSP16	-	80.4	58.2	67.6	141.1	47.5	81.4	59.9	68.8	140.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400C3-625AXSP16	-	91.9	67.3	77.6	158.2	-	92.9	69.2	79	157.3	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400C3-632AXSP16	-	88	64	74.2	153.5	-	89.3	66	75.6	152.6	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400C9-425AXSP16	44.60	79.6	57.9	67.1	139.1	47.4	80.4	59.4	68.1	138.4	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400C9-432AXSP16	40.70	74	53.5	62.2	130.5	43.4	74.8	54.9	63.1	129.7	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400C9-525AXSP16	47.80	85.4	62.3	72	148.2	51	86.3	63.9	73.2	147.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400C9-532AXSP16	-	80.4	58.2	67.6	141.1	47.5	81.4	59.9	68.8	140.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400C9-625AXSP16	-	91.9	67.3	77.6	158.2	-	92.9	69.2	79	157.3	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400C9-632AXSP16	-	88	64	74.2	153.5	-	89.3	66	75.6	152.6	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K3-425AXSP16	42.80	76.6	55.7	64.6	133.8	45.5	77.3	57	65.5	133.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K3-432AXSP16	39.10	71.2	51.4	59.8	125.5	41.8	72.1	52.8	60.8	125	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K3-525AXSP16	45.80	81.9	59.7	69.1	142.2	49	82.8	61.3	70.2	141.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K3-532AXSP16	-	77.3	56	65	135.5	45.6	78.3	57.6	66.2	134.8	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K3-625AXSP16	-	88.2	64.5	74.6	151.9	-	89.3	66.5	75.8	150.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K3-632AXSP16	-	84.5	61.4	71.2	147.4	-	85.7	63.3	72.5	146.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K9-425AXSP16	42.80	76.6	55.7	64.6	133.8	45.5	77.3	57	65.5	133.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K9-432AXSP16	39.10	71.2	51.4	59.8	125.5	41.8	72.1	52.8	60.8	125	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K9-525AXSP16	45.80	81.9	59.7	69.1	142.2	49	82.8	61.3	70.2	141.4	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K9-532AXSP16	-	77.3	56	65	135.5	45.6	78.3	57.6	66.2	134.8	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K9-625AXSP16	-	88.2	64.5	74.6	151.9	-	89.3	66.5	75.8	150.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K9-632AXSP16	-	84.5	61.4	71.2	147.4	-	85.7	63.3	72.5	146.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K3-425AXSP16	43.50	77.9	56.7	65.6	136.2	46.3	78.7	58.1	66.7	135.5	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K3-432AXSP16	39.90	72.5	52.4	60.9	127.9	42.6	73.4	53.8	61.9	127.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB400K3-525AXSP16	46.60	83.3	60.8	70.3	144.6	49.8	84.3	62.4	71.4	143.8	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K3-532AXSP16	-	78.6	56.9	66.1	137.9	46.5	79.6	58.5	67.3	137.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB400K3-625AXSP16	-	89.7	65.6	75.8	154.5	-	90.8	67.5	77	153.6	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB400K3-632AXSP16	-	86	62.4	72.4	149.8	-	87.1	64.4	73.8	148.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550B3-425AXSP16	47.60	84.4	61.7	71.5	148	50.4	85.4	63.2	72.5	147.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550B3-432AXSP16	43.50	78.6	57	66.3	138.7	46.4	79.6	58.5	67.3	138.4	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550B3-525AXSP16	50.90	90.6	66.1	76.4	157	54.2	91.6	67.9	77.7	156.5	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550B3-532AXSP16	47.20	85.4	61.9	71.9	149.8	50.6	86.6	63.6	73.1	149.1	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550B3-625AXSP16	-	97.2	71.2	82.2	167.4	58.8	98.6	73.3	83.7	166.7	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550B3-632AXSP16	-	93.4	67.9	78.8	162.7	-	94.8	70	80.2	161.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550C2-425AXSP16	50.40	88.9	65.1	75.4	156.1	53.2	90	66.7	76.4	155.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550C2-432AXSP16	45.80	82.4	59.9	69.6	145.8	48.7	83.4	61.4	70.6	145.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550C2-525AXSP16	54.30	96	70.3	81.3	166.9	57.6	97	72	82.5	166.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550C2-532AXSP16	50.10	90.2	65.4	76	158.1	53.4	91.2	67.2	77.2	157.5	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550C2-625AXSP16	58.90	104.2	76.4	88.1	179.4	62.9	105.5	78.5	89.5	178.5	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550C2-632AXSP16	-	99.4	72.3	83.8	172.9	59.3	100.7	74.4	85.2	172.1	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550C3-425AXSP16	50.40	88.9	65.1	75.4	156.1	53.2	90	66.7	76.4	155.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550C3-432AXSP16	45.80	82.4	59.9	69.6	145.8	48.7	83.4	61.4	70.6	145.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550C3-442AXSP16	54.30	96	70.3	81.3	166.9	57.6	97	72	82.5	166.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550C3-525AXSP16	50.10	90.2	65.4	76	158.1	53.4	91.2	67.2	77.2	157.5	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550C3-532AXSP16	58.90	104.2	76.4	88.1	179.4	62.9	105.5	78.5	89.5	178.5	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550C3-625AXSP16	-	99.4	72.3	83.8	172.9	59.3	100.7	74.4	85.2	172.1	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550C3-632AXSP16	-	99.4	72.3	83.8	172.9	59.3	100.7	74.4	85.2	172.1	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550C4-425AXSP16	50.40	88.9	65.1	75.4	156.1	53.2	90	66.7	76.4	155.3	113	19.8	1-1/2"	90	13	1-1/2"	135		



EAW-VD1551PB550K4-532AXSP16	47.50	86	62.3	72.3	150.7	50.9	87	64.1	73.6	150.1	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K4-625AXSP16	-	98.7	72.3	83.5	169.8	59.6	99.9	74.3	84.9	168.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K4-632AXSP16	-	94.3	68.6	79.5	164.2	-	95.6	70.7	81	163.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K5-425AXSP16	47.90	85	62.1	71.9	148.8	50.7	85.8	63.6	73	148.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550K5-432AXSP16	43.70	79	57.3	66.5	139.3	46.5	79.9	58.8	67.5	138.9	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550K5-525AXSP16	51.40	91.3	66.7	77.2	158.6	54.7	92.4	68.4	78.3	157.9	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K5-532AXSP16	47.50	86	62.3	72.3	150.7	50.9	87	64.1	73.6	150.1	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K5-625AXSP16	-	98.7	72.3	83.5	169.8	59.6	99.9	74.3	84.9	168.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K5-632AXSP16	-	94.3	68.6	79.5	164.2	-	95.6	70.7	81	163.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K8-425AXSP16	47.90	85	62.1	71.9	148.8	50.7	85.8	63.6	73	148.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550K8-432AXSP16	43.70	79	57.3	66.5	139.3	46.5	79.9	58.8	67.5	138.9	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550K8-525AXSP16	51.40	91.3	66.7	77.2	158.6	54.7	92.4	68.4	78.3	157.9	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K8-532AXSP16	47.50	86	62.3	72.3	150.7	50.9	87	64.1	73.6	150.1	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K8-625AXSP16	-	98.7	72.3	83.5	169.8	59.6	99.9	74.3	84.9	168.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K8-632AXSP16	-	94.3	68.6	79.5	164.2	-	95.6	70.7	81	163.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K9-425AXSP16	47.90	85	62.1	71.9	148.8	50.7	85.8	63.6	73	148.3	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550K9-432AXSP16	43.70	79	57.3	66.5	139.3	46.5	79.9	58.8	67.5	138.9	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550K9-525AXSP16	51.40	91.3	66.7	77.2	158.6	54.7	92.4	68.4	78.3	157.9	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K9-532AXSP16	47.50	86	62.3	72.3	150.7	50.9	87	64.1	73.6	150.1	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550K9-625AXSP16	-	98.7	72.3	83.5	169.8	59.6	99.9	74.3	84.9	168.9	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550K9-632AXSP16	-	94.3	68.6	79.5	164.2	-	95.6	70.7	81	163.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550R3-425AXSP16	49.20	87	63.7	73.7	152.6	52	87.9	65.2	74.7	151.9	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550R3-432AXSP16	44.90	80.9	58.7	68.2	142.9	47.8	81.9	60.3	69.2	142.4	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB550R3-525AXSP16	52.80	93.6	68.4	79.1	162.6	56	94.7	70.1	80.3	161.9	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550R3-532AXSP16	48.80	88.1	63.9	74.2	154.4	52.1	89.3	65.6	75.4	153.9	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB550R3-625AXSP16	57.10	101.3	74.1	85.5	174.2	61.2	102.4	76.2	87	173.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB550R3-632AXSP16	-	96.6	70.4	81.6	168.4	57.7	98	72.4	83	167.7	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C2-425AXSP16	53.60	94.1	69.2	79.8	165.6	56.5	95.3	70.9	81	165.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C2-432AXSP16	48.90	87.4	63.6	73.9	154.6	51.8	88.4	65.3	75	154.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C2-525AXSP16	57.70	101.4	74.4	86	176.6	61.1	102.6	76.4	87.3	176.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C2-532AXSP16	53.30	95.4	69.4	80.5	167.6	56.7	96.6	71.3	81.8	167	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C2-625AXSP16	62.40	110	80.6	93.1	189.3	66.6	111.4	82.9	94.6	188.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C2-632AXSP16	58.60	105.2	76.6	88.6	183	62.9	106.6	78.7	90.2	182.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C3-425AXSP16	53.60	94.1	69.2	79.8	165.6	56.5	95.3	70.9	81	165.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C3-432AXSP16	48.90	87.4	63.6	73.9	154.6	51.8	88.4	65.3	75	154.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C3-525AXSP16	57.70	101.4	74.4	86	176.6	61.1	102.6	76.4	87.3	176.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C3-532AXSP16	53.30	95.4	69.4	80.5	167.6	56.7	96.6	71.3	81.8	167	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C3-625AXSP16	62.40	110	80.6	93.1	189.3	66.6	111.4	82.9	94.6	188.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C3-632AXSP16	58.60	105.2	76.6	88.6	183	62.9	106.6	78.7	90.2	182.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C4-425AXSP16	53.60	94.1	69.2	79.8	165.6	56.5	95.3	70.9	81	165.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C4-432AXSP16	48.90	87.4	63.6	73.9	154.6	51.8	88.4	65.3	75	154.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C4-525AXSP16	57.70	101.4	74.4	86	176.6	61.1	102.6	76.4	87.3	176.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C4-532AXSP16	53.30	95.4	69.4	80.5	167.6	56.7	96.6	71.3	81.8	167	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C4-625AXSP16	62.40	110	80.6	93.1	189.3	66.6	111.4	82.9	94.6	188.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C4-632AXSP16	58.60	105.2	76.6	88.6	183	62.9	106.6	78.7	90.2	182.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C5-425AXSP16	53.60	94.1	69.2	79.8	165.6	56.5	95.3	70.9	81	165.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C5-432AXSP16	48.90	87.4	63.6	73.9	154.6	51.8	88.4	65.3	75	154.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C5-525AXSP16	57.70	101.4	74.4	86	176.6	61.1	102.6	76.4	87.3	176.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C5-532AXSP16	53.30	95.4	69.4	80.5	167.6	56.7	96.6	71.3	81.8	167	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C5-625AXSP16	62.40	110	80.6	93.1	189.3	66.6	111.4	82.9	94.6	188.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C5-632AXSP16	58.60	105.2	76.6	88.6	183	62.9	106.6	78.7	90.2	182.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C8-425AXSP16	53.60	94.1	69.2	79.8	165.6	56.5	95.3	70.9	81	165.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C8-432AXSP16	48.90	87.4	63.6	73.9	154.6	51.8	88.4	65.3	75	154.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C8-525AXSP16	57.70	101.4	74.4	86	176.6	61.1	102.6	76.4	87.3	176.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C8-532AXSP16	53.30	95.4	69.4	80.5	167.6	56.7	96.6	71.3	81.8	167	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C8-625AXSP16	62.40	110	80.6	93.1	189.3	66.6	111.4	82.9	94.6	188.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C8-632AXSP16	58.60	105.2	76.6	88.6	183	62.9	106.6	78.7	90.2	182.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C9-425AXSP16	53.60	94.1	69.2	79.8	165.6	56.5	95.3	70.9	81	165.1	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C9-432AXSP16	48.90	87.4	63.6	73.9	154.6	51.8	88.4	65.3	75	154.2	113	19.8	1-1/2"	90	13	1-1/2"	135	27.8	1-1/2"
EAW-VD1551PB750C9-525AXSP16	57.70	101.4	74.4	86	176.6	61.1	102.6	76.4	87.3	176.2	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C9-532AXSP16	53.30	95.4	69.4	80.5	167.6	56.7	96.6	71.3	81.8	167	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD1551PB750C9-625AXSP16	62.40	110	80.6	93.1	189.3	66.6	111.4	82.9	94.6	188.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750C9-632AXSP16	58.60	105.2	76.6	88.6	183	62.9	106.6	78.7	90.2	182.4	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD1551PB750K2-425AXSP16</																			



EAW-VD15S1PB750R3-525AXSP16	54.10	95.7	70.1	80.9	166.5	57.5	96.9	71.8	82.3	166	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD15S1PB750R3-532AXSP16	50.10	90.3	65.5	76	158.3	53.5	91.5	67.3	77.2	157.7	135	21.3	1-1/2"	108	14	1-1/2"	162	25.3	2"
EAW-VD15S1PB750R3-625AXSP16	58.50	103.6	75.8	87.6	178	62.6	104.9	78	89.1	177.5	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD15S1PB750R3-632AXSP16	-	99.1	72.1	83.5	172.4	59.2	100.3	74.3	85	171.8	169	19	2"	135	15.8	1-1/2"	203	26.7	2"
EAW-VD15S1P370C2-425AXSP16	57.00	94.3	70.8	80.6	161	58.6	94.4	71.4	80.8	159.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C2-432AXSP16	52.40	87.8	65.5	75	151	53.8	87.9	66	75.1	149.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C2-525AXSP16	61.80	101.9	76.6	87.2	171.9	63.5	101.8	77.1	87.3	170.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C2-532AXSP16	57.60	96.1	71.6	81.8	163.7	59.3	96.1	72.4	82	161.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C2-625AXSP16	67.50	110.6	83.2	94.4	184.1	69.5	110.4	83.9	94.6	181.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C2-632AXSP16	63.70	105.7	79.2	90.1	178	65.7	105.6	79.9	90.3	175.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C4-425AXSP16	57.00	94.3	70.8	80.6	161	58.6	94.4	71.4	80.8	159.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C4-432AXSP16	52.40	87.8	65.5	75	151	53.8	87.9	66	75.1	149.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C4-525AXSP16	61.80	101.9	76.6	87.2	171.9	63.5	101.8	77.1	87.3	170.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C4-532AXSP16	57.60	96.1	71.6	81.8	163.7	59.3	96.1	72.4	82	161.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C4-625AXSP16	67.50	110.6	83.2	94.4	184.1	69.5	110.4	83.9	94.6	181.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C4-632AXSP16	63.70	105.7	79.2	90.1	178	65.7	105.6	79.9	90.3	175.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C5-425AXSP16	57.00	94.3	70.8	80.6	161	58.6	94.4	71.4	80.8	159.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C5-432AXSP16	52.40	87.8	65.5	75	151	53.8	87.9	66	75.1	149.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C5-525AXSP16	61.80	101.9	76.6	87.2	171.9	63.5	101.8	77.1	87.3	170.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C5-532AXSP16	57.60	96.1	71.6	81.8	163.7	59.3	96.1	72.4	82	161.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C5-625AXSP16	67.50	110.6	83.2	94.4	184.1	69.5	110.4	83.9	94.6	181.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C5-632AXSP16	63.70	105.7	79.2	90.1	178	65.7	105.6	79.9	90.3	175.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C8-425AXSP16	57.00	94.3	70.8	80.6	161	58.6	94.4	71.4	80.8	159.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C8-432AXSP16	52.40	87.8	65.5	75	151	53.8	87.9	66	75.1	149.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370C8-525AXSP16	61.80	101.9	76.6	87.2	171.9	63.5	101.8	77.1	87.3	170.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C8-532AXSP16	57.60	96.1	71.6	81.8	163.7	59.3	96.1	72.4	82	161.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370C8-625AXSP16	67.50	110.6	83.2	94.4	184.1	69.5	110.4	83.9	94.6	181.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370C8-632AXSP16	63.70	105.7	79.2	90.1	178	65.7	105.6	79.9	90.3	175.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K2-425AXSP16	54.80	90.7	68.1	77.6	154.8	56.3	90.8	68.6	77.8	153	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K2-432AXSP16	50.50	84.8	63.1	72.2	145.5	51.9	84.9	63.7	72.4	143.9	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K2-525AXSP16	59.30	97.7	73.4	83.5	164.8	61	97.8	74	83.7	163	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K2-532AXSP16	55.20	92.4	68.9	78.6	157.1	56.9	92.4	69.5	78.9	155.5	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K2-625AXSP16	64.50	105.7	79.6	90.4	176	66.5	105.5	80.3	90.5	173.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K2-632AXSP16	61.00	101.3	75.9	86.3	170.6	63	101.3	76.6	86.6	168.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K4-425AXSP16	54.80	90.7	68.1	77.6	154.8	56.3	90.8	68.6	77.8	153	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K4-432AXSP16	50.50	84.8	63.1	72.2	145.5	51.9	84.9	63.7	72.4	143.9	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K4-525AXSP16	59.30	97.7	73.4	83.5	164.8	61	97.8	74	83.7	163	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K4-532AXSP16	55.20	92.4	68.9	78.6	157.1	56.9	92.4	69.5	78.9	155.5	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K4-625AXSP16	64.50	105.7	79.6	90.4	176	66.5	105.5	80.3	90.5	173.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K4-632AXSP16	61.00	101.3	75.9	86.3	170.6	63	101.3	76.6	86.6	168.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K5-425AXSP16	54.80	90.7	68.1	77.6	154.8	56.3	90.8	68.6	77.8	153	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K5-432AXSP16	50.50	84.8	63.1	72.2	145.5	51.9	84.9	63.7	72.4	143.9	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K5-525AXSP16	59.30	97.7	73.4	83.5	164.8	61	97.8	74	83.7	163	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K5-532AXSP16	55.20	92.4	68.9	78.6	157.1	56.9	92.4	69.5	78.9	155.5	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K5-625AXSP16	64.50	105.7	79.6	90.4	176	66.5	105.5	80.3	90.5	173.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K5-632AXSP16	61.00	101.3	75.9	86.3	170.6	63	101.3	76.6	86.6	168.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K8-425AXSP16	54.80	90.7	68.1	77.6	154.8	56.3	90.8	68.6	77.8	153	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K8-432AXSP16	50.50	84.8	63.1	72.2	145.5	51.9	84.9	63.7	72.4	143.9	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P370K8-525AXSP16	59.30	97.7	73.4	83.5	164.8	61	97.8	74	83.7	163	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K8-532AXSP16	55.20	92.4	68.9	78.6	157.1	56.9	92.4	69.5	78.9	155.5	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P370K8-625AXSP16	64.50	105.7	79.6	90.4	176	66.5	105.5	80.3	90.5	173.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P370K8-632AXSP16	61.00	101.3	75.9	86.3	170.6	63	101.3	76.6	86.6	168.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P400B3-425AXSP16	55.60	92	69	78.6	156.8	57.1	92.1	69.6	78.7	155.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P400B3-432AXSP16	51.20	85.8	64	73.2	147.4	52.7	85.9	64.6	73.4	146	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P400B3-525AXSP16	60.10	99	74.4	84.7	167.3	61.8	99.1	75.1	84.8	165.3	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P400B3-532AXSP16	56.00	93.7	69.8	79.7	159.4	57.8	93.7	70.5	80	157.7	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P400B3-625AXSP16	65.30	106.9	80.5	91.5	178.1	67.3	106.9	81.3	91.7	176.1	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P400B3-632AXSP16	61.80	102.8	76.8	87.6	172.9	63.9	102.7	77.6	87.9	171	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P400C3-425AXSP16	57.00	94.3	70.8	80.6	161	58.6	94.4	71.4	80.8	159.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P400C3-432AXSP16	52.40	87.8	65.5	75	151	53.8	87.9	66	75.1	149.3	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P400C3-525AXSP16	61.80	101.9	76.6	87.2	171.9	63.5	101.8	77.1	87.3	170.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P400C3-532AXSP16	57.60	96.1	71.6	81.8	163.7	59.3	96.1	72.4	82	161.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P400C3-625AXSP16	67.50	110.6	83.2	94.4	184.1														

EAW-VD15S1PI550C3-432AXSP16	59.00	98.4	73.6	83.9	169.6	60.5	98.5	74.2	84.1	168.2	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C3-525AXSP16	70.10	115	86.8	98.4	195	72	115.1	87.4	98.6	193.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C3-532AXSP16	65.00	107.9	80.8	92.2	184.7	66.7	108.1	81.5	92.4	182.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C3-625AXSP16	76.90	125.6	94.8	107.6	210	79	125.4	95.5	107.8	207.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C3-632AXSP16	72.30	119.7	89.7	102.1	202	74.4	119.6	90.5	102.4	199.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C4-425AXSP16	64.40	106.1	79.7	90.5	181.8	65.9	106.2	80.3	90.8	180.1	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C4-432AXSP16	59.00	98.4	73.6	83.9	169.6	60.5	98.5	74.2	84.1	168.2	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C4-525AXSP16	70.10	115	86.8	98.4	195	72	115.1	87.4	98.6	193.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C4-532AXSP16	65.00	107.9	80.8	92.2	184.7	66.7	108.1	81.5	92.4	182.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C4-625AXSP16	76.90	125.6	94.8	107.6	210	79	125.4	95.5	107.8	207.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C4-632AXSP16	72.30	119.7	89.7	102.1	202	74.4	119.6	90.5	102.4	199.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C5-425AXSP16	64.40	106.1	79.7	90.5	181.8	65.9	106.2	80.3	90.8	180.1	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C5-432AXSP16	59.00	98.4	73.6	83.9	169.6	60.5	98.5	74.2	84.1	168.2	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C5-525AXSP16	70.10	115	86.8	98.4	195	72	115.1	87.4	98.6	193.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C5-532AXSP16	65.00	107.9	80.8	92.2	184.7	66.7	108.1	81.5	92.4	182.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C5-625AXSP16	76.90	125.6	94.8	107.6	210	79	125.4	95.5	107.8	207.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C5-632AXSP16	72.30	119.7	89.7	102.1	202	74.4	119.6	90.5	102.4	199.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C8-425AXSP16	64.40	106.1	79.7	90.5	181.8	65.9	106.2	80.3	90.8	180.1	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C8-432AXSP16	59.00	98.4	73.6	83.9	169.6	60.5	98.5	74.2	84.1	168.2	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C8-525AXSP16	70.10	115	86.8	98.4	195	72	115.1	87.4	98.6	193.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C8-532AXSP16	65.00	107.9	80.8	92.2	184.7	66.7	108.1	81.5	92.4	182.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C8-625AXSP16	76.90	125.6	94.8	107.6	210	79	125.4	95.5	107.8	207.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C8-632AXSP16	72.30	119.7	89.7	102.1	202	74.4	119.6	90.5	102.4	199.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550C9-425AXSP16	64.40	106.1	79.7	90.5	181.8	65.9	106.2	80.3	90.8	180.1	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C9-432AXSP16	59.00	98.4	73.6	83.9	169.6	60.5	98.5	74.2	84.1	168.2	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550C9-525AXSP16	70.10	115	86.8	98.4	195	72	115.1	87.4	98.6	193.1	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C9-625AXSP16	65.00	107.9	80.8	92.2	184.7	66.7	108.1	81.5	92.4	182.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550C9-632AXSP16	76.90	125.6	94.8	107.6	210	79	125.4	95.5	107.8	207.8	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K2-425AXSP16	61.60	101.5	76.4	86.7	173.9	63.2	101.8	77	87	172	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K2-432AXSP16	56.60	94.6	70.6	80.6	163	58.1	94.7	71.2	80.8	161.4	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K2-532AXSP16	66.90	109.7	82.6	93.9	185.9	68.6	109.8	83.3	94.1	183.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K2-625AXSP16	73.00	119.2	90	102	199.2	75.1	119.2	90.7	102.2	197	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K2-632AXSP16	68.80	114.1	85.4	97.2	192.3	70.9	114	86.3	97.5	190.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K3-425AXSP16	61.60	101.5	76.4	86.7	173.9	63.2	101.8	77	87	172	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K3-432AXSP16	56.60	94.6	70.6	80.6	163	58.1	94.7	71.2	80.8	161.4	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K3-525AXSP16	66.90	109.7	82.6	93.9	185.9	68.6	109.8	83.3	94.1	183.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K3-532AXSP16	62.10	103.3	77.3	88.2	176.5	63.8	103.5	78	88.5	174.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K3-625AXSP16	73.00	119.2	90	102	199.2	75.1	119.2	90.7	102.2	197	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K3-632AXSP16	68.80	114.1	85.4	97.2	192.3	70.9	114	86.3	97.5	190.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K4-425AXSP16	61.60	101.5	76.4	86.7	173.9	63.2	101.8	77	87	172	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K4-432AXSP16	56.60	94.6	70.6	80.6	163	58.1	94.7	71.2	80.8	161.4	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K4-525AXSP16	66.90	109.7	82.6	93.9	185.9	68.6	109.8	83.3	94.1	183.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K4-532AXSP16	62.10	103.3	77.3	88.2	176.5	63.8	103.5	78	88.5	174.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K4-625AXSP16	73.00	119.2	90	102	199.2	75.1	119.2	90.7	102.2	197	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K4-632AXSP16	68.80	114.1	85.4	97.2	192.3	70.9	114	86.3	97.5	190.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K5-425AXSP16	61.60	101.5	76.4	86.7	173.9	63.2	101.8	77	87	172	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K5-432AXSP16	56.60	94.6	70.6	80.6	163	58.1	94.7	71.2	80.8	161.4	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K5-525AXSP16	66.90	109.7	82.6	93.9	185.9	68.6	109.8	83.3	94.1	183.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K5-532AXSP16	62.10	103.3	77.3	88.2	176.5	63.8	103.5	78	88.5	174.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K5-625AXSP16	73.00	119.2	90	102	199.2	75.1	119.2	90.7	102.2	197	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K5-632AXSP16	68.80	114.1	85.4	97.2	192.3	70.9	114	86.3	97.5	190.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K8-425AXSP16	61.60	101.5	76.4	86.7	173.9	63.2	101.8	77	87	172	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K8-432AXSP16	56.60	94.6	70.6	80.6	163	58.1	94.7	71.2	80.8	161.4	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K8-525AXSP16	66.90	109.7	82.6	93.9	185.9	68.6	109.8	83.3	94.1	183.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K8-532AXSP16	62.10	103.3	77.3	88.2	176.5	63.8	103.5	78	88.5	174.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K8-625AXSP16	73.00	119.2	90	102	199.2	75.1	119.2	90.7	102.2	197	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K8-632AXSP16	68.80	114.1	85.4	97.2	192.3	70.9	114	86.3	97.5	190.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K9-425AXSP16	61.60	101.5	76.4	86.7	173.9	63.2	101.8	77	87	172	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K9-432AXSP16	56.60	94.6	70.6	80.6	163	58.1	94.7	71.2	80.8	161.4	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1PI550K9-525AXSP16	66.90	109.7	82.6	93.9	185.9	68.6	109.8	83.3	94.1	183.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K9-532AXSP16	62.10	103.3	77.3	88.2	176.5	63.8	103.5	78	88.5	174.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1PI550K9-625AXSP16	73.00	119.2	90	102	199.2	75.1	119.2	90.7	102.2	197	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PI550K9-632AXSP16	68.80	114.1	85.4	97.2	1														

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1P1750C9-425AXSP16	69.20	113.7	85.4	97	-	70.8	114	86.1	97.4	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750C9-432AXSP16	63.40	105.5	78.8	89.9	182.3	65.1	105.7	79.5	90.1	181	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750C9-525AXSP16	75.30	123.1	92.9	105.3	209.5	77.2	123.4	93.6	105.7	205	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750C9-532AXSP16	69.80	115.6	86.8	98.8	198.2	71.6	115.9	87.6	99	196.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750C9-625AXSP16	82.50	134.4	101.6	115.3	225.4	84.9	134.5	102.5	115.6	223.1	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750C9-632AXSP16	77.60	128.2	96.3	109.6	216.9	80	128.4	97.2	109.9	215	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K2-425AXSP16	66.90	110	82.6	93.9	-	68.5	110.3	83.3	94.2	187	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K2-432AXSP16	61.40	102.2	76.4	87.1	176.5	63	102.4	77	87.4	175	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K2-525AXSP16	72.60	118.9	89.7	101.7	202	74.4	119.1	90.4	102	200	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K2-532AXSP16	67.40	111.9	83.8	95.5	191.4	69.2	112.1	84.6	95.9	189.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K2-625AXSP16	79.40	129.3	97.6	110.8	216.5	81.6	129.3	98.5	111.2	214.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K2-632AXSP16	74.90	123.6	92.8	105.8	209.2	77.1	123.7	93.6	106	207	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K3-425AXSP16	66.90	110	82.6	93.9	-	68.5	110.3	83.3	94.2	187	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K3-432AXSP16	61.40	102.2	76.4	87.1	176.5	63	102.4	77	87.4	175	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K3-525AXSP16	72.60	118.9	89.7	101.7	202	74.4	119.1	90.4	102	200	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K3-532AXSP16	67.40	111.9	83.8	95.5	191.4	69.2	112.1	84.6	95.9	189.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K3-625AXSP16	79.40	129.3	97.6	110.8	216.5	81.6	129.3	98.5	111.2	214.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K3-632AXSP16	74.90	123.6	92.8	105.8	209.2	77.1	123.7	93.6	106	207	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K4-425AXSP16	66.90	110	82.6	93.9	-	68.5	110.3	83.3	94.2	187	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K4-432AXSP16	61.40	102.2	76.4	87.1	176.5	63	102.4	77	87.4	175	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K4-525AXSP16	72.60	118.9	89.7	101.7	202	74.4	119.1	90.4	102	200	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K4-532AXSP16	67.40	111.9	83.8	95.5	191.4	69.2	112.1	84.6	95.9	189.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K5-425AXSP16	79.40	129.3	97.6	110.8	216.5	81.6	129.3	98.5	111.2	214.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K5-632AXSP16	74.90	123.6	92.8	105.8	209.2	77.1	123.7	93.6	106	207	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K8-425AXSP16	66.90	110	82.6	93.9	-	68.5	110.3	83.3	94.2	187	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K8-432AXSP16	61.40	102.2	76.4	87.1	176.5	63	102.4	77	87.4	175	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750K8-525AXSP16	72.60	118.9	89.7	101.7	202	74.4	119.1	90.4	102	200	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K8-532AXSP16	67.40	111.9	83.8	95.5	191.4	69.2	112.1	84.6	95.9	189.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K9-425AXSP16	79.40	129.3	97.6	110.8	216.5	81.6	129.3	98.5	111.2	214.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K9-432AXSP16	74.90	123.6	92.8	105.8	209.2	77.1	123.7	93.6	106	207	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K9-525AXSP16	72.60	118.9	89.7	101.7	202	74.4	119.1	90.4	102	200	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K9-532AXSP16	67.40	111.9	83.8	95.5	191.4	69.2	112.1	84.6	95.9	189.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750K9-625AXSP16	79.40	129.3	97.6	110.8	216.5	81.6	129.3	98.5	111.2	214.4	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750K9-632AXSP16	74.90	123.6	92.8	105.8	209.2	77.1	123.7	93.6	106	207	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750R3-425AXSP16	65.40	107.6	80.9	91.9	184.5	67	107.9	81.5	92.2	183	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750R3-432AXSP16	60.00	100.1	74.9	85.4	172.7	61.7	100.3	75.5	85.6	171.5	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD15S1P1750R3-525AXSP16	70.80	116.1	87.7	99.4	197.2	72.7	116.3	88.4	99.6	195.2	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750R3-532AXSP16	65.90	109.4	81.9	93.5	187.4	67.8	109.6	82.8	93.8	185.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD15S1P1750R3-625AXSP16	77.40	126.2	95.3	108.1	211.1	79.6	126.3	96.2	108.4	209	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1P1750R3-632AXSP16	73.00	120.9	90.6	103.2	204.2	75.3	121	91.5	103.6	202.1	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD15S1PK370C2-425AXSP16	49.30	85.1	62.8	72.2	147.3	51.5	85.6	63.9	73	146.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C2-432AXSP16	45.20	79.2	58	67	138.2	47.4	79.7	59.1	67.6	137.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C2-525AXSP16	53.20	91.7	67.6	77.7	157.1	55.8	92.2	68.9	78.4	156	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C2-625AXSP16	49.30	86.3	63.3	73	149.5	51.9	87	64.6	73.8	148.4	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C2-632AXSP16	57.70	99	73.4	84.1	168.2	60.8	99.6	74.8	84.9	166.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD15S1PK370C2-632AXSP16	-	94.7	69.8	80.2	162.8	57.5	95.4	71.3	81.2	161.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD15S1PK370C4-425AXSP16	49.30	85.1	62.8	72.2	147.3	51.5	85.6	63.9	73	146.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C4-432AXSP16	45.20	79.2	58	67	138.2	47.4	79.7	59.1	67.6	137.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C4-525AXSP16	53.20	91.7	67.6	77.7	157.1	55.8	92.2	68.9	78.4	156	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C4-532AXSP16	49.30	86.3	63.3	73	149.5	51.9	87	64.6	73.8	148.4	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C4-625AXSP16	57.70	99	73.4	84.1	168.2	60.8	99.6	74.8	84.9	166.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD15S1PK370C4-632AXSP16	-	94.7	69.8	80.2	162.8	57.5	95.4	71.3	81.2	161.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD15S1PK370C5-425AXSP16	49.30	85.1	62.8	72.2	147.3	51.5	85.6	63.9	73	146.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C5-432AXSP16	45.20	79.2	58	67	138.2	47.4	79.7	59.1	67.6	137.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C5-525AXSP16	53.20	91.7	67.6	77.7	157.1	55.8	92.2	68.9	78.4	156	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C5-532AXSP16	49.30	86.3	63.3	73	149.5	51.9	87	64.6	73.8	148.4	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C5-625AXSP16	57.70	99	73.4	84.1	168.2	60.8	99.6	74.8	84.9	166.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD15S1PK370C5-632AXSP16	-	94.7	69.8	80.2	162.8	57.5	95.4	71.3	81.2	161.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD15S1PK370C8-425AXSP16	49.30	85.1	62.8	72.2	147.3	51.5	85.6	63.9	73	146.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C8-432AXSP16	45.20	79.2	58	67	138.2	47.4	79.7	59.1	67.6	137.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD15S1PK370C8-525AXSP16	53.20	91.7	67.6	77.7	157.1	55.8	92.2	68.9	78.4	156	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD15S1PK370C8-532AXSP16	49.30	86.3	63.3	73	149.5	51.9	87	64.6	73.8	148.4	135	22.							



EAW-VD1551PK400B3-632AXSP16	-	91.8	67.6	77.8	157.7	-	92.4	69	78.7	156.3	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400C3-425AXSP16	49.30	85.1	62.8	72.2	147.3	51.5	85.6	63.9	73	146.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400C3-432AXSP16	45.20	79.2	58	67	138.2	47.4	79.7	59.1	67.6	137.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400C3-525AXSP16	53.20	91.7	67.6	77.7	157.1	55.8	92.2	68.9	78.4	156	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400C3-532AXSP16	49.30	86.3	63.3	73	149.5	51.9	87	64.6	73.8	148.4	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400C3-625AXSP16	57.70	99	73.4	84.1	168.2	60.8	99.6	74.8	84.9	166.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400C3-632AXSP16	-	94.7	69.8	80.2	162.8	57.5	95.4	71.3	81.2	161.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400C9-425AXSP16	49.30	85.1	62.8	72.2	147.3	51.5	85.6	63.9	73	146.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400C9-432AXSP16	45.20	79.2	58	67	138.2	47.4	79.7	59.1	67.6	137.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400C9-525AXSP16	53.20	91.7	67.6	77.7	157.1	55.8	92.2	68.9	78.4	156	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400C9-532AXSP16	49.30	86.3	63.3	73	149.5	51.9	87	64.6	73.8	148.4	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400C9-625AXSP16	57.70	99	73.4	84.1	168.2	60.8	99.6	74.8	84.9	166.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400C9-632AXSP16	-	94.7	69.8	80.2	162.8	57.5	95.4	71.3	81.2	161.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400K3-425AXSP16	47.30	81.8	60.3	69.4	141.6	49.5	82.4	61.4	70.1	140.5	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400K3-432AXSP16	43.40	76.3	55.8	64.4	132.9	45.6	76.8	56.9	65.1	132.1	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400K3-525AXSP16	50.90	88	64.9	74.6	150.8	53.5	88.5	66.1	75.2	149.6	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400K3-532AXSP16	47.30	83	60.8	70.2	143.7	49.9	83.5	62	70.9	142.5	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400K9-632AXSP16	-	94.7	70.2	80.5	161	58.2	95.4	71.6	81.4	159.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400K3-632AXSP16	-	90.9	66.8	76.9	156.1	-	91.5	68.3	77.9	154.9	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400K9-432AXSP16	47.30	81.8	60.3	69.4	141.6	49.5	82.4	61.4	70.1	140.5	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400K9-432AXSP16	43.40	76.3	55.8	64.4	132.9	45.6	76.8	56.9	65.1	132.1	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400K9-525AXSP16	50.90	88	64.9	74.6	150.8	53.5	88.5	66.1	75.2	149.6	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400K9-625AXSP16	47.30	83	60.8	70.2	143.7	49.9	83.5	62	70.9	142.5	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400K9-625AXSP16	-	94.7	70.2	80.5	161	58.2	95.4	71.6	81.4	159.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400K9-632AXSP16	-	90.9	66.8	76.9	156.1	-	91.5	68.3	77.9	154.9	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400R3-425AXSP16	48.30	83.4	61.5	70.7	144.2	50.5	83.9	62.6	71.4	143.3	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400R3-432AXSP16	44.30	77.7	56.9	65.6	135.6	46.5	78.3	58	66.4	134.7	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK400R3-525AXSP16	51.90	89.6	66.1	76	153.6	54.5	90.2	67.4	76.7	152.4	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400R3-532AXSP16	48.20	84.6	62	71.4	146.3	50.8	85.1	63.3	72.3	145.3	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK400R3-625AXSP16	-	96.4	71.5	82	163.9	59.3	97.2	73	82.8	162.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK400R3-632AXSP16	-	92.6	68	78.3	158.9	-	93.3	69.6	79.2	157.8	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0B3-425AXSP16	52.90	90.7	67.1	77.2	157.4	55.1	91.4	68.3	77.9	156.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0B3-432AXSP16	48.40	84.5	62	71.6	147.7	50.7	85.2	63.2	72.4	146.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0B3-525AXSP16	56.90	97.5	72.2	82.9	167.7	59.6	98.2	73.5	83.7	166.6	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0B3-532AXSP16	52.80	92.1	67.6	77.9	159.6	55.5	92.8	68.9	78.9	158.6	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0B3-625AXSP16	61.50	105.3	78	89.5	179	64.8	106.1	79.7	90.5	177.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0B3-632AXSP16	58.10	101.1	74.4	85.5	173.6	61.4	101.9	76.1	86.7	172.4	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C2-425AXSP16	55.70	95.3	70.7	81.1	165.8	58	95.9	71.8	81.8	164.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C2-432AXSP16	50.80	88.4	65	75	154.5	53.1	89	66.1	75.7	153.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C2-525AXSP16	60.30	103.1	76.4	87.8	177.5	63	103.8	77.8	88.6	176.2	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C2-532AXSP16	55.80	96.9	71.2	82.2	168	58.4	97.6	72.6	82.9	167.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C2-625AXSP16	65.80	112.5	83.4	95.5	191	69	113.2	84.9	96.4	189.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C2-632AXSP16	61.80	107.1	78.9	90.8	184.1	65	107.9	80.5	91.6	182.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C3-425AXSP16	55.70	95.3	70.7	81.1	165.8	58	95.9	71.8	81.8	164.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C3-432AXSP16	50.80	88.4	65	75	154.5	53.1	89	66.1	75.7	153.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C3-525AXSP16	60.30	103.1	76.4	87.8	177.5	63	103.8	77.8	88.6	176.2	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C3-532AXSP16	55.80	96.9	71.2	82.2	168	58.4	97.6	72.6	82.9	167.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C3-625AXSP16	65.80	112.5	83.4	95.5	191	69	113.2	84.9	96.4	189.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C3-632AXSP16	61.80	107.1	78.9	90.8	184.1	65	107.9	80.5	91.6	182.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C4-425AXSP16	55.70	95.3	70.7	81.1	165.8	58	95.9	71.8	81.8	164.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C4-432AXSP16	50.80	88.4	65	75	154.5	53.1	89	66.1	75.7	153.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C4-525AXSP16	60.30	103.1	76.4	87.8	177.5	63	103.8	77.8	88.6	176.2	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C4-532AXSP16	55.80	96.9	71.2	82.2	168	58.4	97.6	72.6	82.9	167.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C4-625AXSP16	65.80	112.5	83.4	95.5	191	69	113.2	84.9	96.4	189.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C4-632AXSP16	61.80	107.1	78.9	90.8	184.1	65	107.9	80.5	91.6	182.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C5-425AXSP16	55.70	95.3	70.7	81.1	165.8	58	95.9	71.8	81.8	164.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C5-432AXSP16	50.80	88.4	65	75	154.5	53.1	89	66.1	75.7	153.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C5-525AXSP16	60.30	103.1	76.4	87.8	177.5	63	103.8	77.8	88.6	176.2	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C5-532AXSP16	55.80	96.9	71.2	82.2	168	58.4	97.6	72.6	82.9	167.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK5S0C5-625AXSP16	65.80	112.5	83.4	95.5	191	69	113.2	84.9	96.4	189.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C5-632AXSP16	61.80	107.1	78.9	90.8	184.1	65	107.9	80.5	91.6	182.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK5S0C8-425AXSP16	55.70	95.3	70.7	81.1	165.8	58	95.9	71.8	81.8	164.6	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK5S0C8-432AXSP16	50.80	88.4	65	75	154.5	53.1	89	66.1	75.7	153.6									

EAW-VD1551PK550K8-625AXSP16	62.20	106.4	78.9	90.4	180.7	65.4	107.2	80.4	91.3	179.3	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK550K8-632AXSP16	58.50	101.7	74.9	86.1	174.7	61.7	102.6	76.6	87.1	173.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK550K9-425AXSP16	53.10	91.1	67.5	77.5	158.1	55.4	91.8	68.6	78.2	157.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK550K9-432AXSP16	48.60	84.7	62.2	71.8	148.1	50.8	85.4	63.4	72.5	147.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK550K9-525AXSP16	57.30	98.2	72.7	83.5	168.7	59.9	98.9	74	84.2	167.5	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK550K9-532AXSP16	53.10	92.6	67.9	78.3	160.4	55.7	93.2	69.3	79.2	159.3	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK550K9-625AXSP16	62.20	106.4	78.9	90.4	180.7	65.4	107.2	80.4	91.3	179.3	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK550K9-632AXSP16	58.50	101.7	74.9	86.1	174.7	61.7	102.6	76.6	87.1	173.6	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK550R3-425AXSP16	54.50	93.5	69.3	79.4	162.4	56.9	94.1	70.4	80.1	161.4	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK550R3-432AXSP16	49.90	86.9	63.9	73.7	151.9	52.2	87.5	65	74.4	151.1	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK550R3-525AXSP16	58.80	100.7	74.6	85.7	173.2	61.5	101.4	76	86.5	172	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK550R3-532AXSP16	54.50	94.9	69.7	80.4	164.7	57.2	95.7	71.1	81.2	163.6	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK550R3-625AXSP16	63.90	109.2	80.9	92.8	185.6	67.1	109.9	82.5	93.7	184.3	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK550R3-632AXSP16	60.10	104.4	76.9	88.4	179.5	63.4	105.2	78.6	89.4	178.2	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C2-425AXSP16	59.50	101.4	75.4	86.3	176.8	61.9	102.2	76.5	87	175.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C2-432AXSP16	54.30	94.1	69.4	79.9	164.9	56.7	94.9	70.7	80.6	164.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C2-525AXSP16	64.30	109.4	81.4	93.2	189	67.1	110.4	82.8	94.1	187.9	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C2-532AXSP16	59.50	102.9	75.9	87.4	179	62.3	103.8	77.4	88.4	178.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C2-625AXSP16	70.10	119.2	88.6	101.3	202.8	73.4	120	90.2	102.6	201.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C2-632AXSP16	65.90	113.9	84	96.6	195.7	69.3	114.8	85.7	97.6	194.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C3-425AXSP16	59.50	101.4	75.4	86.3	176.8	61.9	102.2	76.5	87	175.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C3-432AXSP16	54.30	94.1	69.4	79.9	164.9	56.7	94.9	70.7	80.6	164.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C3-525AXSP16	64.30	109.4	81.4	93.2	189	67.1	110.4	82.8	94.1	187.9	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C3-532AXSP16	59.50	102.9	75.9	87.4	179	62.3	103.8	77.4	88.4	178.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C3-625AXSP16	70.10	119.2	88.6	101.3	202.8	73.4	120	90.2	102.6	201.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C3-632AXSP16	65.90	113.9	84	96.6	195.7	69.3	114.8	85.7	97.6	194.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C4-425AXSP16	59.50	101.4	75.4	86.3	176.8	61.9	102.2	76.5	87	175.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C4-432AXSP16	54.30	94.1	69.4	79.9	164.9	56.7	94.9	70.7	80.6	164.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C4-525AXSP16	64.30	109.4	81.4	93.2	189	67.1	110.4	82.8	94.1	187.9	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C4-532AXSP16	59.50	102.9	75.9	87.4	179	62.3	103.8	77.4	88.4	178.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C4-625AXSP16	70.10	119.2	88.6	101.3	202.8	73.4	120	90.2	102.6	201.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C4-632AXSP16	65.90	113.9	84	96.6	195.7	69.3	114.8	85.7	97.6	194.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C5-425AXSP16	59.50	101.4	75.4	86.3	176.8	61.9	102.2	76.5	87	175.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C5-432AXSP16	54.30	94.1	69.4	79.9	164.9	56.7	94.9	70.7	80.6	164.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C5-525AXSP16	64.30	109.4	81.4	93.2	189	67.1	110.4	82.8	94.1	187.9	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C5-532AXSP16	59.50	102.9	75.9	87.4	179	62.3	103.8	77.4	88.4	178.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C5-625AXSP16	70.10	119.2	88.6	101.3	202.8	73.4	120	90.2	102.6	201.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C5-632AXSP16	65.90	113.9	84	96.6	195.7	69.3	114.8	85.7	97.6	194.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C8-425AXSP16	59.50	101.4	75.4	86.3	176.8	61.9	102.2	76.5	87	175.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C8-432AXSP16	54.30	94.1	69.4	79.9	164.9	56.7	94.9	70.7	80.6	164.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C8-525AXSP16	64.30	109.4	81.4	93.2	189	67.1	110.4	82.8	94.1	187.9	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C8-532AXSP16	59.50	102.9	75.9	87.4	179	62.3	103.8	77.4	88.4	178.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C8-625AXSP16	70.10	119.2	88.6	101.3	202.8	73.4	120	90.2	102.6	201.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C8-632AXSP16	65.90	113.9	84	96.6	195.7	69.3	114.8	85.7	97.6	194.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C9-425AXSP16	59.50	101.4	75.4	86.3	176.8	61.9	102.2	76.5	87	175.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C9-432AXSP16	54.30	94.1	69.4	79.9	164.9	56.7	94.9	70.7	80.6	164.2	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750C9-525AXSP16	64.30	109.4	81.4	93.2	189	67.1	110.4	82.8	94.1	187.9	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C9-532AXSP16	59.50	102.9	75.9	87.4	179	62.3	103.8	77.4	88.4	178.1	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750C9-625AXSP16	70.10	119.2	88.6	101.3	202.8	73.4	120	90.2	102.6	201.7	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750C9-632AXSP16	65.90	113.9	84	96.6	195.7	69.3	114.8	85.7	97.6	194.5	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750K2-425AXSP16	57.40	98.2	72.8	83.5	170.8	59.8	98.9	74	84.2	169.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750K2-432AXSP16	52.50	91.1	67.1	77.3	159.6	54.9	91.9	68.4	78.1	158.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750K2-525AXSP16	61.90	105.6	78.4	90	182	64.7	106.5	79.9	90.9	181	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750K2-532AXSP16	57.40	99.5	73.3	84.5	172.8	60.1	100.3	74.7	85.5	172	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750K2-625AXSP16	67.30	114.8	85.2	97.5	195.1	70.7	115.7	86.8	98.6	193.9	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750K2-632AXSP16	63.30	109.8	80.9	93	188.6	66.7	110.6	82.6	94.1	187.4	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750K2-632AXSP16	57.40	98.2	72.8	83.5	170.8	59.8	98.9	74	84.2	169.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750K3-425AXSP16	52.50	91.1	67.1	77.3	159.6	54.9	91.9	68.4	78.1	158.9	113	21.1	1-1/2"	90	13.9	1-1/2"	135	29.6	1-1/2"
EAW-VD1551PK750K3-432AXSP16	61.90	105.6	78.4	90	182	64.7	106.5	79.9	90.9	181	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750K3-525AXSP16	57.40	99.5	73.3	84.5	172.8	60.1	100.3	74.7	85.5	172	135	22.6	1-1/2"	108	14.9	1-1/2"	162	27.2	2"
EAW-VD1551PK750K3-532AXSP16	67.30	114.8	85.2	97.5	195.1	70.7	115.7	86.8	98.6	193.9	169	20.4	2"	135	16.7	1-1/2"	203	28.6	2"
EAW-VD1551PK750K3-625AXSP16	63.30	109.8	80.																

EAW-VD1551ZB370C4-532AXSP16	-	91.2	65.9	76.7	160.5	-	92.2	67.8	77.9	159	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370C4-625AXSP16	-	105.1	76.7	88.7	181.3	-	106.1	79	90.1	179.5	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370C4-632AXSP16	-	100.1	-	84.4	175	-	101.3	-	85.8	173.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370C5-425AXSP16	49.20	89	64.5	74.9	155.7	52.6	89.8	66.2	76	154.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370C5-432AXSP16	-	82.4	59.3	69.2	145.6	-	83.2	61	70.2	144.7	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370C5-525AXSP16	-	97.1	70.7	81.9	169	-	98.1	72.6	83.2	167.4	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370C5-532AXSP16	-	91.2	65.9	76.7	160.5	-	92.2	67.8	77.9	159	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370C5-625AXSP16	-	105.1	76.7	88.7	181.3	-	106.1	79	90.1	179.5	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370C5-632AXSP16	-	100.1	-	84.4	175	-	101.3	-	85.8	173.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370C8-425AXSP16	49.20	89	64.5	74.9	155.7	52.6	89.8	66.2	76	154.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370C8-432AXSP16	-	82.4	59.3	69.2	145.6	-	83.2	61	70.2	144.7	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370C8-525AXSP16	-	97.1	70.7	81.9	169	-	98.1	72.6	83.2	167.4	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370C8-532AXSP16	-	91.2	65.9	76.7	160.5	-	92.2	67.8	77.9	159	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370C8-625AXSP16	-	105.1	76.7	88.7	181.3	-	106.1	79	90.1	179.5	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370C8-632AXSP16	-	100.1	-	84.4	175	-	101.3	-	85.8	173.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K2-425AXSP16	-	85.5	62	72	149.7	50.5	86.3	63.6	73	148.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K2-432AXSP16	-	79.4	57.1	66.6	140.4	-	80.3	58.8	67.7	139.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K2-525AXSP16	-	93.1	67.7	78.5	162	-	94.1	69.6	79.7	160.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K2-532AXSP16	-	87.6	63.2	73.6	154.2	-	88.6	65.2	74.9	153	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K2-625AXSP16	-	100.4	-	84.9	173.4	-	101.5	75.5	86.2	171.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K2-632AXSP16	-	96	-	80.7	167.6	-	97.1	-	82.3	166.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K4-425AXSP16	-	85.5	62	72	149.7	50.5	86.3	63.6	73	148.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K4-432AXSP16	-	79.4	57.1	66.6	140.4	-	80.3	58.8	67.7	139.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K4-525AXSP16	-	93.1	67.7	78.5	162	-	94.1	69.6	79.7	160.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K4-532AXSP16	-	87.6	63.2	73.6	154.2	-	88.6	65.2	74.9	153	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K4-625AXSP16	-	100.4	-	84.9	173.4	-	101.5	75.5	86.2	171.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K4-632AXSP16	-	96	-	80.7	167.6	-	97.1	-	82.3	166.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K5-425AXSP16	-	85.5	62	72	149.7	50.5	86.3	63.6	73	148.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K5-432AXSP16	-	79.4	57.1	66.6	140.4	-	80.3	58.8	67.7	139.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K5-525AXSP16	-	93.1	67.7	78.5	162	-	94.1	69.6	79.7	160.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K5-532AXSP16	-	87.6	63.2	73.6	154.2	-	88.6	65.2	74.9	153	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K5-625AXSP16	-	100.4	-	84.9	173.4	-	101.5	75.5	86.2	171.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K5-632AXSP16	-	96	-	80.7	167.6	-	97.1	-	82.3	166.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K8-425AXSP16	-	85.5	62	72	149.7	50.5	86.3	63.6	73	148.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K8-432AXSP16	-	79.4	57.1	66.6	140.4	-	80.3	58.8	67.7	139.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB370K8-525AXSP16	-	93.1	67.7	78.5	162	-	94.1	69.6	79.7	160.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K8-532AXSP16	-	87.6	63.2	73.6	154.2	-	88.6	65.2	74.9	153	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB370K8-625AXSP16	-	100.4	-	84.9	173.4	-	101.5	75.5	86.2	171.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB370K8-632AXSP16	-	96	-	80.7	167.6	-	97.1	-	82.3	166.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400B3-425AXSP16	-	86.8	62.9	72.9	151.8	51.2	87.6	64.6	74.1	150.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400B3-432AXSP16	-	80.5	58	67.6	142.4	-	81.4	59.7	68.6	141.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400B3-525AXSP16	-	94.4	68.7	79.7	164.2	-	95.4	70.6	80.9	162.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400B3-532AXSP16	-	88.8	64.1	74.7	156.3	-	89.8	66.2	75.9	155	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400B3-625AXSP16	-	101.7	-	85.9	175.3	-	102.8	76.5	87.3	173.7	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400B3-632AXSP16	-	97.2	-	81.9	169.9	-	98.4	-	83.4	168.5	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400C3-425AXSP16	49.20	89	64.5	74.9	155.7	52.6	89.8	66.2	76	154.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400C3-432AXSP16	-	82.4	59.3	69.2	145.6	-	83.2	61	70.2	144.7	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400C3-525AXSP16	-	97.1	70.7	81.9	169	-	98.1	72.6	83.2	167.4	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400C3-532AXSP16	-	91.2	65.9	76.7	160.5	-	92.2	67.8	77.9	159	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400C3-625AXSP16	-	105.1	76.7	88.7	181.3	-	106.1	79	90.1	179.5	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400C3-632AXSP16	-	100.1	-	84.4	175	-	101.3	-	85.8	173.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400C9-425AXSP16	49.20	89	64.5	74.9	155.7	52.6	89.8	66.2	76	154.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400C9-432AXSP16	-	82.4	59.3	69.2	145.6	-	83.2	61	70.2	144.7	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400C9-525AXSP16	-	97.1	70.7	81.9	169	-	98.1	72.6	83.2	167.4	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400C9-532AXSP16	-	91.2	65.9	76.7	160.5	-	92.2	67.8	77.9	159	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400C9-625AXSP16	-	105.1	76.7	88.7	181.3	-	106.1	79	90.1	179.5	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400C9-632AXSP16	-	100.1	-	84.4	175	-	101.3	-	85.8	173.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400K3-425AXSP16	-	85.5	62	72	149.7	50.5	86.3	63.6	73	148.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400K3-432AXSP16	-	79.4	57.1	66.6	140.4	-	80.3	58.8	67.7	139.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400K3-525AXSP16	-	93.1	67.7	78.5	162	-	94.1	69.6	79.7	160.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400K3-532AXSP16	-	87.6	63.2	73.6	154.2	-	88.6	65.2	74.9	153	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400K3-625AXSP16	-	100.4	-	84.9	173.4	-	101.5	75.5	86.2	171.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400K3-632AXSP16	-	96	-	80.7	167.6	-	97.1	-	82.3	166.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB400K9-425AXSP16	-	85.5	62	72	149.7	50.5	86.3	63.6	73	148.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400K9-432AXSP16	-	79.4	57.1	66.6	140.4	-	80.3	58.8	67.7	139.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB400K9-525AXSP16	-	93.1	67.7	78.5	162	-	94.1	69.6	79.7	160.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB400K9-532AXSP16	-	87.6	63.2	73.6	154.2	-	88.6	65.2	74.9	153	180	19.6	2"	144	12.9				

EAW-VD1551ZB550C5-525AXSP16	61.60	110.3	80.3	93	191.5	65.8	111.3	82.3	94.2	189.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550C5-532AXSP16	-	103	74.6	86.8	180.9	60.7	104.2	76.6	88	179.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550C5-625AXSP16	-	119.9	87.7	101.4	206.7	-	121	90	102.8	204.8	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550C5-632AXSP16	-	113.8	82.7	96	198.5	-	115	85	97.5	196.8	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550C8-425AXSP16	56.00	100.3	73	84.5	175.6	59.4	101.2	74.6	85.7	174.3	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550C8-432AXSP16	50.80	92.6	66.8	77.8	163.5	54.2	93.7	68.6	78.9	162.5	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550C8-525AXSP16	61.60	110.3	80.3	93	191.5	65.8	111.3	82.3	94.2	189.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550C8-532AXSP16	-	103	74.6	86.8	180.9	60.7	104.2	76.6	88	179.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550C8-625AXSP16	-	119.9	87.7	101.4	206.7	-	121	90	102.8	204.8	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550C8-632AXSP16	-	113.8	82.7	96	198.5	-	115	85	97.5	196.8	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550C9-425AXSP16	56.00	100.3	73	84.5	175.6	59.4	101.2	74.6	85.7	174.3	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550C9-432AXSP16	50.80	92.6	66.8	77.8	163.5	54.2	93.7	68.6	78.9	162.5	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550C9-525AXSP16	61.60	110.3	80.3	93	191.5	65.8	111.3	82.3	94.2	189.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550C9-532AXSP16	-	103	74.6	86.8	180.9	60.7	104.2	76.6	88	179.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550C9-625AXSP16	-	119.9	87.7	101.4	206.7	-	121	90	102.8	204.8	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550C9-632AXSP16	-	113.8	82.7	96	198.5	-	115	85	97.5	196.8	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K2-425AXSP16	53.40	96.1	69.8	81	168.1	56.9	97.1	71.5	82.1	166.9	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K2-432AXSP16	-	89	64.1	74.7	157.1	52.1	89.9	65.9	75.8	156.1	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K2-525AXSP16	-	105	76.5	88.6	182.4	62.6	106.1	78.5	89.8	180.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K2-532AXSP16	-	98.4	71.2	82.9	173.1	-	99.6	73.3	84.2	171.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K2-625AXSP16	-	113.8	83.1	96.1	196	-	114.8	85.5	97.5	194.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K2-632AXSP16	-	108.3	78.6	91.3	188.9	-	109.6	81	92.8	187.4	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K3-425AXSP16	53.40	96.1	69.8	81	168.1	56.9	97.1	71.5	82.1	166.9	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K3-432AXSP16	-	89	64.1	74.7	157.1	52.1	89.9	65.9	75.8	156.1	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K3-525AXSP16	-	105	76.5	88.6	182.4	62.6	106.1	78.5	89.8	180.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K3-532AXSP16	-	98.4	71.2	82.9	173.1	-	99.6	73.3	84.2	171.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K3-625AXSP16	-	113.8	83.1	96.1	196	-	114.8	85.5	97.5	194.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K3-632AXSP16	-	108.3	78.6	91.3	188.9	-	109.6	81	92.8	187.4	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K4-425AXSP16	53.40	96.1	69.8	81	168.1	56.9	97.1	71.5	82.1	166.9	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K4-432AXSP16	-	89	64.1	74.7	157.1	52.1	89.9	65.9	75.8	156.1	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K4-525AXSP16	-	105	76.5	88.6	182.4	62.6	106.1	78.5	89.8	180.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K4-532AXSP16	-	98.4	71.2	82.9	173.1	-	99.6	73.3	84.2	171.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K4-625AXSP16	-	113.8	83.1	96.1	196	-	114.8	85.5	97.5	194.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K4-632AXSP16	-	108.3	78.6	91.3	188.9	-	109.6	81	92.8	187.4	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K5-425AXSP16	53.40	96.1	69.8	81	168.1	56.9	97.1	71.5	82.1	166.9	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K5-432AXSP16	-	89	64.1	74.7	157.1	52.1	89.9	65.9	75.8	156.1	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K5-525AXSP16	-	105	76.5	88.6	182.4	62.6	106.1	78.5	89.8	180.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K5-532AXSP16	-	98.4	71.2	82.9	173.1	-	99.6	73.3	84.2	171.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K5-625AXSP16	-	113.8	83.1	96.1	196	-	114.8	85.5	97.5	194.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K5-632AXSP16	-	108.3	78.6	91.3	188.9	-	109.6	81	92.8	187.4	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K8-425AXSP16	53.40	96.1	69.8	81	168.1	56.9	97.1	71.5	82.1	166.9	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K8-432AXSP16	-	89	64.1	74.7	157.1	52.1	89.9	65.9	75.8	156.1	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K8-525AXSP16	-	105	76.5	88.6	182.4	62.6	106.1	78.5	89.8	180.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K8-532AXSP16	-	98.4	71.2	82.9	173.1	-	99.6	73.3	84.2	171.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K8-625AXSP16	-	113.8	83.1	96.1	196	-	114.8	85.5	97.5	194.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K8-632AXSP16	-	108.3	78.6	91.3	188.9	-	109.6	81	92.8	187.4	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K9-425AXSP16	53.40	96.1	69.8	81	168.1	56.9	97.1	71.5	82.1	166.9	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K9-432AXSP16	-	89	64.1	74.7	157.1	52.1	89.9	65.9	75.8	156.1	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550K9-525AXSP16	-	105	76.5	88.6	182.4	62.6	106.1	78.5	89.8	180.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K9-532AXSP16	-	98.4	71.2	82.9	173.1	-	99.6	73.3	84.2	171.7	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550K9-625AXSP16	-	113.8	83.1	96.1	196	-	114.8	85.5	97.5	194.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550K9-632AXSP16	-	108.3	78.6	91.3	188.9	-	109.6	81	92.8	187.4	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550R3-425AXSP16	55.00	98.8	71.8	83.2	172.8	58.5	99.7	73.5	84.4	171.7	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550R3-432AXSP16	50.00	91.4	66	76.8	161.4	53.6	92.4	67.8	78	160.5	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB550R3-525AXSP16	60.30	108.1	78.7	91.1	187.5	64.5	109.1	80.8	92.4	186.3	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550R3-532AXSP16	-	101.4	73.4	85.3	177.9	-	102.4	75.4	86.6	176.9	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB550R3-625AXSP16	-	117.1	85.7	99	201.6	-	118.3	88	100.5	200	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB550R3-632AXSP16	-	111.5	81	93.9	194.4	-	112.8	83.4	95.6	193	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750C2-425AXSP16	60.50	107.5	78.6	90.9	188.8	64	108.7	80.3	92.2	187.6	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750C2-432AXSP16	54.90	99.4	72	83.7	175.6	58.4	100.6	73.8	84.9	174.7	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750C2-525AXSP16	66.50	118.5	86.3	99.9	205.5	70.7	119.7	88.6	101.3	204.4	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750C2-532AXSP16	61.10	110.9	80.3	93.2	194.2	65.4	112	82.4	94.6	193.3	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750C2-625AXSP16	-	128.9	94.3	108.9	221.7	77.6	130.1	96.7	110.4	220	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750C2-632AXSP16	-	122.4	89	103.1	213.3	-	123.8	91.4	104.7	211.7	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750C3-425AXSP16	60.50	107.5	78.6	90.9	188.8	64	108.7	80.3	92.2	187.6	146	18.5	2"	117	14.9	1-1/2"	1		

EAW-VD1551ZB750K3-432AXSP16	53.00	96.4	69.6	81	170.2	56.5	97.4	71.4	82.2	169.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K3-525AXSP16	63.90	114.2	83.1	96.3	198.2	68.1	115.2	85.4	97.6	196.8	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K3-532AXSP16	-	107	77.5	90	187.7	63.1	108.2	79.6	91.3	186.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K3-625AXSP16	-	123.7	90.6	104.6	213.1	-	125.1	93.1	106.2	211.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K3-632AXSP16	-	117.9	85.6	99.4	205.4	-	119.2	88.1	100.9	204.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K4-425AXSP16	58.30	104.1	75.8	87.9	182.4	61.8	105.1	77.6	89.1	181.3	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K4-432AXSP16	53.00	96.4	69.6	81	170.2	56.5	97.4	71.4	82.2	169.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K4-525AXSP16	63.90	114.2	83.1	96.3	198.2	68.1	115.2	85.4	97.6	196.8	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K4-532AXSP16	-	107	77.5	90	187.7	63.1	108.2	79.6	91.3	186.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K4-625AXSP16	-	123.7	90.6	104.6	213.1	-	125.1	93.1	106.2	211.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K4-632AXSP16	-	117.9	85.6	99.4	205.4	-	119.2	88.1	100.9	204.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K5-425AXSP16	58.30	104.1	75.8	87.9	182.4	61.8	105.1	77.6	89.1	181.3	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K5-432AXSP16	53.00	96.4	69.6	81	170.2	56.5	97.4	71.4	82.2	169.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K5-525AXSP16	63.90	114.2	83.1	96.3	198.2	68.1	115.2	85.4	97.6	196.8	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K5-532AXSP16	-	107	77.5	90	187.7	63.1	108.2	79.6	91.3	186.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K5-625AXSP16	-	123.7	90.6	104.6	213.1	-	125.1	93.1	106.2	211.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K5-632AXSP16	-	117.9	85.6	99.4	205.4	-	119.2	88.1	100.9	204.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K8-425AXSP16	58.30	104.1	75.8	87.9	182.4	61.8	105.1	77.6	89.1	181.3	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K8-432AXSP16	53.00	96.4	69.6	81	170.2	56.5	97.4	71.4	82.2	169.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K8-525AXSP16	63.90	114.2	83.1	96.3	198.2	68.1	115.2	85.4	97.6	196.8	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K8-532AXSP16	-	107	77.5	90	187.7	63.1	108.2	79.6	91.3	186.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K8-625AXSP16	-	123.7	90.6	104.6	213.1	-	125.1	93.1	106.2	211.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K8-632AXSP16	-	117.9	85.6	99.4	205.4	-	119.2	88.1	100.9	204.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K9-425AXSP16	58.30	104.1	75.8	87.9	182.4	61.8	105.1	77.6	89.1	181.3	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K9-432AXSP16	53.00	96.4	69.6	81	170.2	56.5	97.4	71.4	82.2	169.4	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750K9-525AXSP16	63.90	114.2	83.1	96.3	198.2	68.1	115.2	85.4	97.6	196.8	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K9-532AXSP16	-	107	77.5	90	187.7	63.1	108.2	79.6	91.3	186.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750K9-625AXSP16	-	123.7	90.6	104.6	213.1	-	125.1	93.1	106.2	211.6	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750K9-632AXSP16	-	117.9	85.6	99.4	205.4	-	119.2	88.1	100.9	204.1	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750R3-425AXSP16	57.00	101.9	74.1	85.9	178.3	60.5	102.8	75.9	87.1	177.2	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750R3-432AXSP16	51.80	94.3	68.2	79.3	166.6	55.3	95.4	70	80.5	165.8	146	18.5	2"	117	14.9	1-1/2"	176	25.9	2"
EAW-VD1551ZB750R3-525AXSP16	62.30	111.6	81.2	94	193.5	66.6	112.6	83.3	95.4	192.4	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750R3-532AXSP16	-	104.5	75.6	88	183.7	61.7	105.8	77.8	89.4	182.5	180	19.6	2"	144	12.9	2"	216	27.5	2"
EAW-VD1551ZB750R3-625AXSP16	-	120.7	88.2	101.9	207.7	-	122	90.7	103.5	206.2	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZB750R3-632AXSP16	-	115	83.6	97	200.5	-	116.4	86.1	98.6	199.3	225	21.4	2"	180	14.1	2"	270	24.2	3"
EAW-VD1551ZK017G7-425AXSP16	80.00	136.3	101.2	115.9	238.2	82.9	137	102.6	116.6	236.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK017G7-432AXSP16	72.30	125.1	92.3	106.1	220	75.3	126	93.8	107.1	218.4	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK017G7-525AXSP16	89.40	152	113	129.3	262.8	92.9	152.6	114.6	130.4	260.3	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK017G7-532AXSP16	81.70	141.1	104.1	119.9	245.7	85.2	142	105.7	120.9	243.9	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK017G7-625AXSP16	99.20	168.2	125.2	143.4	286.9	103.4	168.9	127	144.3	284.3	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK017G7-632AXSP16	91.90	158.4	116.8	134.3	272.8	96	159.1	118.9	135.4	270.4	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C2-425AXSP16	54.20	94.5	69.4	79.9	163.5	56.8	95	70.6	80.5	161.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C2-432AXSP16	49.30	87.6	63.9	73.8	152.9	52.2	88.1	65.2	74.6	151.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C2-525AXSP16	-	103.4	76.1	87.5	177.2	62.6	103.8	77.5	88.3	175.3	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C2-532AXSP16	-	97.1	71	82	168.2	-	97.6	72.5	82.8	166.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C2-625AXSP16	-	111.8	82.7	94.9	189.9	-	112.3	84.3	95.7	187.6	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C2-632AXSP16	-	106.6	78.3	90.3	183.2	-	107.2	80	91.2	181.2	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C4-425AXSP16	54.20	94.5	69.4	79.9	163.5	56.8	95	70.6	80.5	161.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C4-432AXSP16	49.30	87.6	63.9	73.8	152.9	52.2	88.1	65.2	74.6	151.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C4-525AXSP16	-	103.4	76.1	87.5	177.2	62.6	103.8	77.5	88.3	175.3	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C4-532AXSP16	-	97.1	71	82	168.2	-	97.6	72.5	82.8	166.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C4-625AXSP16	-	111.8	82.7	94.9	189.9	-	112.3	84.3	95.7	187.6	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C4-632AXSP16	-	106.6	78.3	90.3	183.2	-	107.2	80	91.2	181.2	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C5-425AXSP16	54.20	94.5	69.4	79.9	163.5	56.8	95	70.6	80.5	161.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C5-432AXSP16	49.30	87.6	63.9	73.8	152.9	52.2	88.1	65.2	74.6	151.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C5-525AXSP16	-	103.4	76.1	87.5	177.2	62.6	103.8	77.5	88.3	175.3	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C5-532AXSP16	-	97.1	71	82	168.2	-	97.6	72.5	82.8	166.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C5-625AXSP16	-	111.8	82.7	94.9	189.9	-	112.3	84.3	95.7	187.6	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C5-632AXSP16	-	106.6	78.3	90.3	183.2	-	107.2	80	91.2	181.2	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C8-425AXSP16	54.20	94.5	69.4	79.9	163.5	56.8	95	70.6	80.5	161.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C8-432AXSP16	49.30	87.6	63.9	73.8	152.9	52.2	88.1	65.2	74.6	151.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK370C8-525AXSP16	-	103.4	76.1	87.5	177.2	62.6	103.8	77.5	88.3	175.3	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C8-532AXSP16	-	97.1	71	82	168.2	-	97.6	72.5	82.8	166.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK370C8-625AXSP16	-	111.8	82.7	94.9	189.9	-	112.3	84.3	95.7	187.6	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK370C8-632AXSP16																			

EAW-VD1551ZK400C9-425AXSP16	54.20	94.5	69.4	79.9	163.5	56.8	95	70.6	80.5	161.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400C9-432AXSP16	49.30	87.6	63.9	73.8	152.9	52.2	88.1	65.2	74.6	151.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400C9-525AXSP16	-	103.4	76.1	87.5	177.2	62.6	103.8	77.5	88.3	175.3	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400C9-532AXSP16	-	97.1	71	82	168.2	-	97.6	72.5	82.8	166.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400C9-625AXSP16	-	111.8	82.7	94.9	189.9	-	112.3	84.3	95.7	187.6	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400C9-632AXSP16	-	106.6	78.3	90.3	183.2	-	107.2	80	91.2	181.2	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400K3-425AXSP16	52.00	90.9	66.8	76.9	157.1	54.7	91.4	67.9	77.6	155.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400K3-432AXSP16	-	84.5	61.7	71.3	147.6	50.3	85.1	62.9	72	146.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400K3-525AXSP16	-	99	72.9	83.9	169.9	-	99.5	74.3	84.7	167.9	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400K3-532AXSP16	-	93.2	68.3	78.9	161.8	-	93.9	69.7	79.7	160.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400K3-625AXSP16	-	106.8	79	90.7	181.6	-	107.4	80.7	91.6	179.4	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400K3-632AXSP16	-	102.1	-	86.4	175.8	-	102.8	76.7	87.4	173.8	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400K9-425AXSP16	52.00	90.9	66.8	76.9	157.1	54.7	91.4	67.9	77.6	155.6	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400K9-432AXSP16	-	84.5	61.7	71.3	147.6	50.3	85.1	62.9	72	146.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400K9-525AXSP16	-	99	72.9	83.9	169.9	-	99.5	74.3	84.7	167.9	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400K9-532AXSP16	-	93.2	68.3	78.9	161.8	-	93.9	69.7	79.7	160.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400K9-625AXSP16	-	106.8	79	90.7	181.6	-	107.4	80.7	91.6	179.4	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400K9-632AXSP16	-	102.1	-	86.4	175.8	-	102.8	76.7	87.4	173.8	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400R3-425AXSP16	53.20	93	68.3	78.6	160.6	56	93.4	69.5	79.4	159.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400R3-532AXSP16	-	86.5	63	72.9	150.8	51.4	87	64.3	73.7	149.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK400R3-525AXSP16	-	101.2	74.6	85.8	173.6	61.4	101.8	76.1	86.5	171.9	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400R3-532AXSP16	-	95.4	69.8	80.6	165.4	-	96	71.3	81.5	163.8	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK400R3-625AXSP16	-	109.2	80.9	92.7	185.7	-	109.7	82.5	93.7	183.5	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK400R3-632AXSP16	-	104.4	76.8	88.5	179.6	-	105.2	78.5	89.4	177.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50B3-425AXSP16	58.70	102.1	75.1	86.5	176.4	61.5	102.4	76.3	87.1	174.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50B3-432AXSP16	53.60	94.7	69.1	79.9	165.1	56.4	95.3	70.4	80.6	163.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50B3-525AXSP16	64.50	111.6	82.4	94.6	191.6	67.8	112.3	83.7	95.4	189.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50B3-532AXSP16	-	105	76.9	88.7	181.7	62.9	105.6	78.4	89.6	180.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50B3-625AXSP16	-	120.8	89.4	102.5	205.3	-	121.3	91.1	103.6	203.1	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50B3-632AXSP16	-	115.3	84.7	97.6	198.4	-	116	86.6	98.6	196.2	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C2-425AXSP16	61.50	106.5	78.5	90.4	184.5	64.3	107.1	79.8	91.1	182.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C2-432AXSP16	56.00	98.7	72	83.2	172.1	58.8	99.2	73.3	84	170.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C2-525AXSP16	68.00	117.5	86.5	99.5	201.4	71.2	117.9	88.1	100.2	199.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C2-532AXSP16	62.50	109.8	80.5	92.8	190.1	65.8	110.4	82	93.7	188.4	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C2-625AXSP16	-	127.7	94.6	108.4	216.9	78.2	128.3	96.2	109.3	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C2-632AXSP16	-	121.3	89.1	102.6	208.5	-	122	91.1	103.6	206.3	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C3-425AXSP16	61.50	106.5	78.5	90.4	184.5	64.3	107.1	79.8	91.1	182.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C3-432AXSP16	56.00	98.7	72	83.2	172.1	58.8	99.2	73.3	84	170.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C3-525AXSP16	68.00	117.5	86.5	99.5	201.4	71.2	117.9	88.1	100.2	199.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C3-532AXSP16	62.50	109.8	80.5	92.8	190.1	65.8	110.4	82	93.7	188.4	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C3-625AXSP16	-	127.7	94.6	108.4	216.9	78.2	128.3	96.2	109.3	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C3-632AXSP16	-	121.3	89.1	102.6	208.5	-	122	91.1	103.6	206.3	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C4-425AXSP16	61.50	106.5	78.5	90.4	184.5	64.3	107.1	79.8	91.1	182.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C4-432AXSP16	56.00	98.7	72	83.2	172.1	58.8	99.2	73.3	84	170.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C4-525AXSP16	68.00	117.5	86.5	99.5	201.4	71.2	117.9	88.1	100.2	199.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C4-532AXSP16	62.50	109.8	80.5	92.8	190.1	65.8	110.4	82	93.7	188.4	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C4-625AXSP16	-	127.7	94.6	108.4	216.9	78.2	128.3	96.2	109.3	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C4-632AXSP16	-	121.3	89.1	102.6	208.5	-	122	91.1	103.6	206.3	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C5-425AXSP16	61.50	106.5	78.5	90.4	184.5	64.3	107.1	79.8	91.1	182.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C5-432AXSP16	56.00	98.7	72	83.2	172.1	58.8	99.2	73.3	84	170.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C5-525AXSP16	68.00	117.5	86.5	99.5	201.4	71.2	117.9	88.1	100.2	199.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C5-532AXSP16	62.50	109.8	80.5	92.8	190.1	65.8	110.4	82	93.7	188.4	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C5-625AXSP16	-	127.7	94.6	108.4	216.9	78.2	128.3	96.2	109.3	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C5-632AXSP16	-	121.3	89.1	102.6	208.5	-	122	91.1	103.6	206.3	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C8-425AXSP16	61.50	106.5	78.5	90.4	184.5	64.3	107.1	79.8	91.1	182.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C8-432AXSP16	56.00	98.7	72	83.2	172.1	58.8	99.2	73.3	84	170.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C8-525AXSP16	68.00	117.5	86.5	99.5	201.4	71.2	117.9	88.1	100.2	199.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C8-532AXSP16	62.50	109.8	80.5	92.8	190.1	65.8	110.4	82	93.7	188.4	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C8-625AXSP16	-	127.7	94.6	108.4	216.9	78.2	128.3	96.2	109.3	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C8-632AXSP16	-	121.3	89.1	102.6	208.5	-	122	91.1	103.6	206.3	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK50C9-425AXSP16	61.50	106.5	78.5	90.4	184.5	64.3	107.1	79.8	91.1	182.9	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C9-432AXSP16	56.00	98.7	72	83.2	172.1	58.8	99.2	73.3	84	170.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK50C9-525AXSP16	68.00	117.5	86.5	99.5	201.4	71.2	117.9	88.1	100.2	199.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C9-532AXSP16	62.50	109.8	80.5	92.8	190.1	65.8	110.4	82	93.7	188.4	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK50C9-625AXSP16	-	127.7	94.6	108.4	216.9	78.2	128.3												

EAW-VD1551ZK550K9-632AXSP16	-	115.7	85	97.8	198.8	-	116.3	86.9	98.9	196.8	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK550R3-425AXSP16	60.70	105.1	77.5	89.3	182.3	63.5	105.8	78.8	89.9	180.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK550R3-432AXSP16	55.40	97.7	71.3	82.4	170.3	58.2	98.3	72.7	83.3	169.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK550R3-525AXSP16	66.70	115.3	85	97.7	197.6	70.1	115.9	86.6	98.5	195.8	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK550R3-532AXSP16	61.60	108.3	79.3	91.5	187.7	65	109	80.9	92.4	186.1	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK550R3-625AXSP16	-	125.1	92.5	106.2	212.5	76.6	125.7	94.3	107.1	210.2	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK550R3-632AXSP16	-	119.1	87.6	100.8	204.8	-	119.8	89.5	101.9	202.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C2-425AXSP16	66.60	114.6	84.7	97.6	199.3	69.4	115.4	86	98.2	197.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C2-432AXSP16	60.60	106.2	77.7	89.8	185.4	63.5	106.8	79.2	90.6	184.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C2-525AXSP16	73.50	126.4	93.4	107.3	217	76.9	127.1	94.9	108.2	215.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C2-532AXSP16	67.70	118.5	86.9	100.1	205.3	71.1	119.2	88.4	101.1	203.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C2-625AXSP16	80.40	137.9	102.2	117	234.3	84.5	138.6	104	118	232	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C2-632AXSP16	-	130.9	96.3	110.9	224.9	79.3	131.6	98.3	112	222.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C3-425AXSP16	66.60	114.6	84.7	97.6	199.3	69.4	115.4	86	98.2	197.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C3-432AXSP16	60.60	106.2	77.7	89.8	185.4	63.5	106.8	79.2	90.6	184.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C3-525AXSP16	73.50	126.4	93.4	107.3	217	76.9	127.1	94.9	108.2	215.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C3-532AXSP16	67.70	118.5	86.9	100.1	205.3	71.1	119.2	88.4	101.1	203.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C3-625AXSP16	80.40	137.9	102.2	117	234.3	84.5	138.6	104	118	232	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C3-632AXSP16	-	130.9	96.3	110.9	224.9	79.3	131.6	98.3	112	222.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C4-425AXSP16	66.60	114.6	84.7	97.6	199.3	69.4	115.4	86	98.2	197.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C4-432AXSP16	60.60	106.2	77.7	89.8	185.4	63.5	106.8	79.2	90.6	184.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C4-525AXSP16	73.50	126.4	93.4	107.3	217	76.9	127.1	94.9	108.2	215.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C4-532AXSP16	67.70	118.5	86.9	100.1	205.3	71.1	119.2	88.4	101.1	203.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C4-625AXSP16	80.40	137.9	102.2	117	234.3	84.5	138.6	104	118	232	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C4-632AXSP16	-	130.9	96.3	110.9	224.9	79.3	131.6	98.3	112	222.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C9-425AXSP16	66.60	114.6	84.7	97.6	199.3	69.4	115.4	86	98.2	197.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C9-432AXSP16	60.60	106.2	77.7	89.8	185.4	63.5	106.8	79.2	90.6	184.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C9-525AXSP16	73.50	126.4	93.4	107.3	217	76.9	127.1	94.9	108.2	215.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C9-532AXSP16	67.70	118.5	86.9	100.1	205.3	71.1	119.2	88.4	101.1	203.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C9-625AXSP16	80.40	137.9	102.2	117	234.3	84.5	138.6	104	118	232	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C9-632AXSP16	-	130.9	96.3	110.9	224.9	79.3	131.6	98.3	112	222.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C8-425AXSP16	66.60	114.6	84.7	97.6	199.3	69.4	115.4	86	98.2	197.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C8-432AXSP16	60.60	106.2	77.7	89.8	185.4	63.5	106.8	79.2	90.6	184.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C8-525AXSP16	73.50	126.4	93.4	107.3	217	76.9	127.1	94.9	108.2	215.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C8-532AXSP16	67.70	118.5	86.9	100.1	205.3	71.1	119.2	88.4	101.1	203.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C8-625AXSP16	80.40	137.9	102.2	117	234.3	84.5	138.6	104	118	232	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C8-632AXSP16	-	130.9	96.3	110.9	224.9	79.3	131.6	98.3	112	222.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C9-425AXSP16	66.60	114.6	84.7	97.6	199.3	69.4	115.4	86	98.2	197.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C9-432AXSP16	60.60	106.2	77.7	89.8	185.4	63.5	106.8	79.2	90.6	184.2	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750C9-525AXSP16	73.50	126.4	93.4	107.3	217	76.9	127.1	94.9	108.2	215.2	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C9-532AXSP16	67.70	118.5	86.9	100.1	205.3	71.1	119.2	88.4	101.1	203.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750C9-625AXSP16	80.40	137.9	102.2	117	234.3	84.5	138.6	104	118	232	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750C9-632AXSP16	-	130.9	96.3	110.9	224.9	79.3	131.6	98.3	112	222.9	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K2-425AXSP16	64.30	110.9	82	94.4	192.5	67.1	111.7	83.2	95.1	191.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K2-432AXSP16	58.70	102.9	75.3	87.1	179.9	61.5	103.7	76.7	87.9	178.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K2-525AXSP16	70.70	121.9	90	103.4	209.3	74.1	122.6	91.5	104.3	207.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750K2-532AXSP16	65.30	114.5	83.8	96.7	198.4	68.7	115.2	85.5	97.7	196.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750K2-625AXSP16	77.20	132.6	98.2	112.6	225.1	81.3	133.2	99.9	113.5	223	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K2-632AXSP16	-	126.2	92.8	106.9	216.9	76.4	127	94.6	107.9	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K3-425AXSP16	64.30	110.9	82	94.4	192.5	67.1	111.7	83.2	95.1	191.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K3-432AXSP16	58.70	102.9	75.3	87.1	179.9	61.5	103.7	76.7	87.9	178.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K3-525AXSP16	70.70	121.9	90	103.4	209.3	74.1	122.6	91.5	104.3	207.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750K3-532AXSP16	65.30	114.5	83.8	96.7	198.4	68.7	115.2	85.5	97.7	196.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750K3-625AXSP16	77.20	132.6	98.2	112.6	225.1	81.3	133.2	99.9	113.5	223	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K3-632AXSP16	-	126.2	92.8	106.9	216.9	76.4	127	94.6	107.9	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K4-425AXSP16	64.30	110.9	82	94.4	192.5	67.1	111.7	83.2	95.1	191.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K4-432AXSP16	58.70	102.9	75.3	87.1	179.9	61.5	103.7	76.7	87.9	178.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K4-525AXSP16	70.70	121.9	90	103.4	209.3	74.1	122.6	91.5	104.3	207.5	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750K4-532AXSP16	65.30	114.5	83.8	96.7	198.4	68.7	115.2	85.5	97.7	196.6	180	20.9	2"	144	13.8	2"	216	29.4	2"
EAW-VD1551ZK750K4-625AXSP16	77.20	132.6	98.2	112.6	225.1	81.3	133.2	99.9	113.5	223	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K4-632AXSP16	-	126.2	92.8	106.9	216.9	76.4	127	94.6	107.9	214.7	225	22.8	2"	180	15	2"	270	26.1	3"
EAW-VD1551ZK750K5-425AXSP16	64.30	110.9	82	94.4	192.5	67.1	111.7	83.2	95.1	191.1	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD1551ZK750K5-432AXSP16	58.70	102.9	75.3	87.1	179.9	61.5	103.7	76.7	87.9	178.5	146	19.8	2"	117	15.7	1-1/2"	176	27.8	2"
EAW-VD155																			

EAW-VD1552PB370C5-625AXSP16	128.80	199	153.1	171.4	-	129.8	198	153	171	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370C5-632AXSP16	122.80	191.6	146.7	164.8	-	123.7	190.6	146.5	164.1	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370C8-425AXSP12	101.80	164.7	124.1	140.8	-	103.5	164.8	124.8	140.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370C8-432AXSP12	93.80	153.1	115	130.8	-	95.6	153.4	115.7	131	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370C8-525AXSP12	112.00	179.6	136.1	153.8	-	114	179.6	137	154.1	300.7	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370C8-532AXSP12	104.40	169.6	128.1	145.2	288.7	106.6	169.9	129	145.4	286.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370C8-625AXSP16	128.80	199	153.1	171.4	-	129.8	198	153	171	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370C8-632AXSP16	122.80	191.6	146.7	164.8	-	123.7	190.6	146.5	164.1	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K2-425AXSP12	98.00	158.4	119.5	135.5	-	99.7	158.7	120.1	135.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K2-432AXSP12	90.40	147.8	111	126.2	-	92.1	147.8	111.7	126.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K2-525AXSP12	107.50	172.8	130.9	147.9	291.3	109.5	172.7	131.7	148.1	288.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K2-532AXSP12	100.50	163.4	123.5	139.8	277.7	102.6	163.6	124.2	139.9	275.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K8-625AXSP16	124.10	191.2	147.2	165	-	124.8	190.3	147	164.2	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K2-632AXSP16	118.10	184.1	141.1	158.4	-	119	183.3	141	157.7	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K4-425AXSP12	98.00	158.4	119.5	135.5	-	99.7	158.7	120.1	135.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K4-432AXSP12	90.40	147.8	111	126.2	-	92.1	147.8	111.7	126.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K4-525AXSP12	107.50	172.8	130.9	147.9	291.3	109.5	172.7	131.7	148.1	288.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K4-532AXSP12	100.50	163.4	123.5	139.8	277.7	102.6	163.6	124.2	139.9	275.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K8-625AXSP16	124.10	191.2	147.2	165	-	124.8	190.3	147	164.2	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K4-632AXSP16	118.10	184.1	141.1	158.4	-	119	183.3	141	157.7	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K5-425AXSP12	98.00	158.4	119.5	135.5	-	99.7	158.7	120.1	135.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K5-432AXSP12	90.40	147.8	111	126.2	-	92.1	147.8	111.7	126.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K5-525AXSP12	107.50	172.8	130.9	147.9	291.3	109.5	172.7	131.7	148.1	288.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K5-532AXSP12	100.50	163.4	123.5	139.8	277.7	102.6	163.6	124.2	139.9	275.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K5-625AXSP16	124.10	191.2	147.2	165	-	124.8	190.3	147	164.2	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K5-632AXSP16	118.10	184.1	141.1	158.4	-	119	183.3	141	157.7	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K8-425AXSP12	98.00	158.4	119.5	135.5	-	99.7	158.7	120.1	135.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K8-432AXSP12	90.40	147.8	111	126.2	-	92.1	147.8	111.7	126.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB370K8-525AXSP12	107.50	172.8	130.9	147.9	291.3	109.5	172.7	131.7	148.1	288.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K8-532AXSP12	100.50	163.4	123.5	139.8	277.7	102.6	163.6	124.2	139.9	275.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB370K8-625AXSP16	124.10	191.2	147.2	165	-	124.8	190.3	147	164.2	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB370K8-632AXSP16	118.10	184.1	141.1	158.4	-	119	183.3	141	157.7	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400B3-425AXSP12	98.90	159.9	120.7	136.6	-	100.7	160.1	121.3	137	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400B3-432AXSP12	91.30	149.3	112.2	127.4	-	93.2	149.4	112.9	127.7	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400B3-525AXSP12	108.20	173.7	131.6	148.9	293	110.3	173.9	132.6	149.3	290.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400B3-532AXSP16	107.20	169.2	128.8	145.1	-	108	168.6	128.8	144.8	-	135	33.2	1-1/2"	108	21.9	1-1/2"	162	42.1	2"
EAW-VD1552PB400B3-625AXSP16	124.30	191.7	147.6	165.2	-	125.3	190.9	147.7	164.8	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400B3-632AXSP16	118.90	185.3	141.9	159.3	-	119.7	184.5	141.9	159	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400C3-425AXSP12	101.80	164.7	124.1	140.8	-	103.5	164.8	124.8	140.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400C3-432AXSP12	93.80	153.1	115	130.8	-	95.6	153.4	115.7	131	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400C3-525AXSP12	112.00	179.6	136.1	153.8	-	114	179.6	137	154.1	300.7	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400C3-532AXSP12	104.40	169.6	128.1	145.2	288.7	106.6	169.9	129	145.4	286.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400C3-625AXSP16	128.80	199	153.1	171.4	-	129.8	198	153	171	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400C3-632AXSP16	122.80	191.6	146.7	164.8	-	123.7	190.6	146.5	164.1	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400C9-425AXSP12	101.80	164.7	124.1	140.8	-	103.5	164.8	124.8	140.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400C9-432AXSP12	93.80	153.1	115	130.8	-	95.6	153.4	115.7	131	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400C9-525AXSP12	112.00	179.6	136.1	153.8	-	114	179.6	137	154.1	300.7	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400C9-532AXSP12	104.40	169.6	128.1	145.2	288.7	106.6	169.9	129	145.4	286.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400C9-625AXSP16	128.80	199	153.1	171.4	-	129.8	198	153	171	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400C9-632AXSP16	122.80	191.6	146.7	164.8	-	123.7	190.6	146.5	164.1	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400K3-425AXSP12	98.00	158.4	119.5	135.5	-	99.7	158.7	120.1	135.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400K3-432AXSP12	90.40	147.8	111	126.2	-	92.1	147.8	111.7	126.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400K3-525AXSP12	107.50	172.8	130.9	147.9	291.3	109.5	172.7	131.7	148.1	288.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400K3-532AXSP12	100.50	163.4	123.5	139.8	277.7	102.6	163.6	124.2	139.9	275.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400K3-625AXSP16	124.10	191.2	147.2	165	-	124.8	190.3	147	164.2	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400K3-632AXSP16	118.10	184.1	141.1	158.4	-	119	183.3	141	157.7	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400K9-425AXSP12	98.00	158.4	119.5	135.5	-	99.7	158.7	120.1	135.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400K9-432AXSP12	90.40	147.8	111	126.2	-	92.1	147.8	111.7	126.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400K9-525AXSP12	107.50	172.8	130.9	147.9	291.3	109.5	172.7	131.7	148.1	288.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400K9-532AXSP12	100.50	163.4	123.5	139.8	277.7	102.6	163.6	124.2	139.9	275.4	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB400K9-625AXSP16	124.10	191.2	147.2	165	-	124.8	190.3	147	164.2	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400K9-632AXSP16	118.10	184.1	141.1	158.4	-	119	183.3	141	157.7	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB400R3-425AXSP12	99.60	161.1	121.5	137.8	-	101.4	161.2	122.2	137.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB400R3-432AXSP12	92.00	150.2	112.9	128.1	-	93.8	150.5	113.7	128.4	-	146	23.2	2"	117	17.8				

EAW-VD1552PB550C8-532AXSP12	117.00	189.7	142.8	162.1	-	119.2	190	143.7	162.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550C8-625AXSP12	137.80	219.3	167	188.3	366.8	140.4	219.4	167.9	188.6	363.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550C8-632AXSP12	130.20	209.8	158.8	179.7	354.2	132.9	210.1	159.9	180.2	351.1	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550C9-425AXSP12	113.30	183.9	138.3	157	-	115.2	184.3	139.3	157.7	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550C9-432AXSP12	104.20	170.3	127.8	145.3	-	106.1	170.6	128.6	145.7	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550C9-525AXSP12	125.60	201.8	152.5	172.7	-	127.9	201.9	153.5	173	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550C9-532AXSP12	117.00	189.7	142.8	162.1	-	119.2	190	143.7	162.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550C9-625AXSP12	137.80	219.3	167	188.3	366.8	140.4	219.4	167.9	188.6	363.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550C9-632AXSP12	130.20	209.8	158.8	179.7	354.2	132.9	210.1	159.9	180.2	351.1	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K2-425AXSP12	108.40	175.7	132.1	150.2	-	110.3	176	133.1	150.5	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K2-432AXSP12	100.10	163.5	122.5	139.3	-	101.8	163.8	123.4	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K2-525AXSP12	119.80	191.8	145.3	164.3	-	121.9	192.1	146.1	164.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K2-625AXSP12	111.60	181.1	136.4	154.7	-	113.7	181.3	137.5	155.2	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K2-625AXSP12	130.70	208.1	158.5	178.6	347.6	133.3	208.1	159.5	179.1	344.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K2-632AXSP16	130.90	204.7	156.4	175.8	-	131.9	203.9	156.5	175.3	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB550K3-425AXSP12	108.40	175.7	132.1	150.2	-	110.3	176	133.1	150.5	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K3-432AXSP12	100.10	163.5	122.5	139.3	-	101.8	163.8	123.4	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K3-525AXSP12	119.80	191.8	145.3	164.3	-	121.9	192.1	146.1	164.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K3-532AXSP12	111.60	181.1	136.4	154.7	-	113.7	181.3	137.5	155.2	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K3-625AXSP12	130.70	208.1	158.5	178.6	347.6	133.3	208.1	159.5	179.1	344.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K3-632AXSP16	130.90	204.7	156.4	175.8	-	131.9	203.9	156.5	175.3	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB550K4-425AXSP12	108.40	175.7	132.1	150.2	-	110.3	176	133.1	150.5	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K4-432AXSP12	100.10	163.5	122.5	139.3	-	101.8	163.8	123.4	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K4-525AXSP12	119.80	191.8	145.3	164.3	-	121.9	192.1	146.1	164.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K4-532AXSP12	111.60	181.1	136.4	154.7	-	113.7	181.3	137.5	155.2	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K4-625AXSP12	130.70	208.1	158.5	178.6	347.6	133.3	208.1	159.5	179.1	344.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K4-632AXSP16	130.90	204.7	156.4	175.8	-	131.9	203.9	156.5	175.3	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB550K5-425AXSP12	108.40	175.7	132.1	150.2	-	110.3	176	133.1	150.5	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K5-432AXSP12	100.10	163.5	122.5	139.3	-	101.8	163.8	123.4	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K5-525AXSP12	119.80	191.8	145.3	164.3	-	121.9	192.1	146.1	164.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K5-532AXSP12	111.60	181.1	136.4	154.7	-	113.7	181.3	137.5	155.2	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K5-625AXSP12	130.70	208.1	158.5	178.6	347.6	133.3	208.1	159.5	179.1	344.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K5-632AXSP16	130.90	204.7	156.4	175.8	-	131.9	203.9	156.5	175.3	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB550K8-425AXSP12	108.40	175.7	132.1	150.2	-	110.3	176	133.1	150.5	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K8-432AXSP12	100.10	163.5	122.5	139.3	-	101.8	163.8	123.4	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K8-525AXSP12	119.80	191.8	145.3	164.3	-	121.9	192.1	146.1	164.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K8-532AXSP12	111.60	181.1	136.4	154.7	-	113.7	181.3	137.5	155.2	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K8-625AXSP12	130.70	208.1	158.5	178.6	347.6	133.3	208.1	159.5	179.1	344.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K8-632AXSP16	130.90	204.7	156.4	175.8	-	131.9	203.9	156.5	175.3	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB550K9-425AXSP12	108.40	175.7	132.1	150.2	-	110.3	176	133.1	150.5	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K9-432AXSP12	100.10	163.5	122.5	139.3	-	101.8	163.8	123.4	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550K9-525AXSP12	119.80	191.8	145.3	164.3	-	121.9	192.1	146.1	164.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K9-532AXSP12	111.60	181.1	136.4	154.7	-	113.7	181.3	137.5	155.2	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550K9-625AXSP12	130.70	208.1	158.5	178.6	347.6	133.3	208.1	159.5	179.1	344.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550K9-632AXSP16	130.90	204.7	156.4	175.8	-	131.9	203.9	156.5	175.3	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD1552PB550R3-425AXSP12	110.80	179.9	135.4	153.7	-	112.8	180.5	136.3	154.2	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550R3-432AXSP12	102.40	167.2	125.4	142.6	-	104.3	167.6	126.4	143.1	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB550R3-525AXSP12	122.50	196.5	148.6	168.2	-	124.7	196.9	149.6	168.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550R3-532AXSP12	114.30	185.4	139.7	158.5	-	116.5	185.8	140.7	158.9	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB550R3-625AXSP12	133.90	213.1	162.4	183	356.2	136.6	213.5	163.3	183.4	353.1	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB550R3-632AXSP12	126.70	204.3	155	175.1	344.6	129.5	204.5	155.9	175.6	341.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750C2-425AXSP12	119.80	194.8	146.4	166.3	-	122	195.3	147.4	167.1	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750C2-432AXSP12	110.30	180.8	135.3	154	-	112.5	181.4	136.4	154.6	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750C2-525AXSP12	132.40	213.1	160.9	182.4	-	134.9	213.7	162.1	182.9	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750C2-532AXSP12	123.70	200.6	151.1	171.4	-	126	201.3	152.1	172	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750C2-625AXSP12	145.30	231.2	175.7	198.3	-	148.3	231.5	177.2	199.1	-	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750C2-632AXSP12	137.60	221.4	167.7	189.7	374.5	140.5	222.1	169	190.3	371.8	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750C3-425AXSP12	119.80	194.8	146.4	166.3	-	122	195.3	147.4	167.1	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750C3-432AXSP12	110.30	180.8	135.3	154	-	112.5	181.4	136.4	154.6	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750C3-525AXSP12	132.40	213.1	160.9	182.4	-	134.9	213.7	162.1	182.9	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750C3-532AXSP12	123.70	200.6	151.1	171.4	-	126	201.3	152.1	172	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750C3-625AXSP12	145.30	231.2	175.7	198.3	-	148.3	231.5	177.2	199.1	-	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750C3-632AXSP12	137.60	221.4	167.7	189.7	374.5	140.5	222.1	169	190.3	371.8	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750C4-425AXSP12	119.80	194.8	146.4	166.3	-	122	195.3	147.4	167.1	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2

EAW-VD1552PB750K4-525AXSP12	127.90	205.9	155.4	176	-	130.5	206.2	156.7	176.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K4-532AXSP12	119.70	193.9	146.1	165.6	-	122.1	194.5	147.2	166.4	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K4-625AXSP12	140.40	223.2	169.9	191.6	373.5	143.1	223.7	171.2	192.3	371	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K4-632AXSP12	132.80	214	162.1	183.2	361.5	135.7	214.4	163.1	183.9	358.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K5-425AXSP12	115.90	188.4	141.7	160.7	-	118	188.8	142.8	161.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750K5-432AXSP12	107.00	174.9	131.2	149.2	-	109.1	175.6	132.2	149.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750K5-525AXSP12	127.90	205.9	155.4	176	-	130.5	206.2	156.7	176.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K5-532AXSP12	119.70	193.9	146.1	165.6	-	122.1	194.5	147.2	166.4	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K5-625AXSP12	140.40	223.2	169.9	191.6	373.5	143.1	223.7	171.2	192.3	371	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K5-632AXSP12	132.80	214	162.1	183.2	361.5	135.7	214.4	163.1	183.9	358.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K8-425AXSP12	115.90	188.4	141.7	160.7	-	118	188.8	142.8	161.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750K8-432AXSP12	107.00	174.9	131.2	149.2	-	109.1	175.6	132.2	149.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750K8-525AXSP12	127.90	205.9	155.4	176	-	130.5	206.2	156.7	176.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K8-532AXSP12	119.70	193.9	146.1	165.6	-	122.1	194.5	147.2	166.4	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K8-625AXSP12	140.40	223.2	169.9	191.6	373.5	143.1	223.7	171.2	192.3	371	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K8-632AXSP12	132.80	214	162.1	183.2	361.5	135.7	214.4	163.1	183.9	358.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K9-425AXSP12	115.90	188.4	141.7	160.7	-	118	188.8	142.8	161.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750K9-432AXSP12	107.00	174.9	131.2	149.2	-	109.1	175.6	132.2	149.8	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750K9-525AXSP12	127.90	205.9	155.4	176	-	130.5	206.2	156.7	176.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K9-532AXSP12	119.70	193.9	146.1	165.6	-	122.1	194.5	147.2	166.4	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750K9-625AXSP12	140.40	223.2	169.9	191.6	373.5	143.1	223.7	171.2	192.3	371	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750K9-632AXSP12	132.80	214	162.1	183.2	361.5	135.7	214.4	163.1	183.9	358.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750R3-425AXSP12	113.50	184.5	138.7	157.5	-	115.7	184.9	139.7	158.1	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750R3-432AXSP12	104.90	171.6	128.6	146.2	-	107	171.9	129.5	146.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD1552PB750R3-432AXSP12	125.30	201	152.2	172.3	-	127.6	201.7	153.3	172.8	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750R3-532AXSP12	117.10	189.9	143	162.3	-	119.5	190.4	144.1	162.8	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD1552PB750R3-625AXSP12	136.80	217.7	165.8	186.9	364.5	139.7	218.2	167	187.6	361.5	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552PB750R3-632AXSP12	129.90	209.3	158.4	179.3	352.8	132.6	209.4	159.7	179.6	350.4	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD1552P370C2-425AXSP08	113.40	187.7	140.9	160.6	321.1	116.5	187.9	142	160.8	317.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552P370C2-432AXSP12	112.70	179.3	136	153.5	-	113.5	178.2	135.7	152.8	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370C2-525AXSP12	135.30	210.9	161.4	181.5	-	135.9	209.4	161.1	180.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C2-532AXSP12	126.50	199	151.7	170.9	-	127.3	197.7	151.3	170	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C2-625AXSP12	148.80	228.4	176.4	197.2	374.1	149.3	226.6	175.7	195.9	368.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C2-632AXSP12	140.80	219.1	168.3	188.7	362	141.5	217.4	167.5	187.4	356.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C4-425AXSP08	113.40	187.7	140.9	160.6	321.1	116.5	187.9	142	160.8	317.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552P370C4-432AXSP12	112.70	179.3	136	153.5	-	113.5	178.2	135.7	152.8	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370C4-525AXSP12	135.30	210.9	161.4	181.5	-	135.9	209.4	161.1	180.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C4-532AXSP12	126.50	199	151.7	170.9	-	127.3	197.7	151.3	170	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C4-625AXSP12	148.80	228.4	176.4	197.2	374.1	149.3	226.6	175.7	195.9	368.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C4-632AXSP12	140.80	219.1	168.3	188.7	362	141.5	217.4	167.5	187.4	356.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C5-425AXSP08	113.40	187.7	140.9	160.6	321.1	116.5	187.9	142	160.8	317.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552P370C5-432AXSP12	112.70	179.3	136	153.5	-	113.5	178.2	135.7	152.8	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370C5-525AXSP12	135.30	210.9	161.4	181.5	-	135.9	209.4	161.1	180.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C5-532AXSP12	126.50	199	151.7	170.9	-	127.3	197.7	151.3	170	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C5-625AXSP12	148.80	228.4	176.4	197.2	374.1	149.3	226.6	175.7	195.9	368.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C5-632AXSP12	140.80	219.1	168.3	188.7	362	141.5	217.4	167.5	187.4	356.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C8-425AXSP08	113.40	187.7	140.9	160.6	321.1	116.5	187.9	142	160.8	317.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552P370C8-432AXSP12	112.70	179.3	136	153.5	-	113.5	178.2	135.7	152.8	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370C8-525AXSP12	135.30	210.9	161.4	181.5	-	135.9	209.4	161.1	180.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C8-532AXSP12	126.50	199	151.7	170.9	-	127.3	197.7	151.3	170	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370C8-625AXSP12	148.80	228.4	176.4	197.2	374.1	149.3	226.6	175.7	195.9	368.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370C8-632AXSP12	140.80	219.1	168.3	188.7	362	141.5	217.4	167.5	187.4	356.6	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370K2-425AXSP12	117.60	185.3	141.2	159.2	-	118.3	184.3	141	158.3	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370K2-432AXSP12	109.10	173	131.2	148.3	-	109.6	171.9	131	147.6	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370K2-525AXSP12	130.00	202.3	155	174.2	-	130.5	200.9	154.6	173.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370K2-532AXSP12	121.80	191.3	146	164.4	-	122.6	190.1	145.6	163.6	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370K2-625AXSP12	142.50	218.8	168.8	189	357.6	143	217	168.2	187.7	352.3	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370K2-632AXSP12	135.10	210.2	161.4	181.1	346.5	135.9	208.5	160.8	179.9	341.7	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370K4-425AXSP12	117.60	185.3	141.2	159.2	-	118.3	184.3	141	158.3	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370K4-432AXSP12	109.10	173	131.2	148.3	-	109.6	171.9	131	147.6	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD1552P370K4-525AXSP12	130.00	202.3	155	174.2	-	130.5	200.9	154.6	173.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370K4-532AXSP12	121.80	191.3	146	164.4	-	122.6	190.1	145.6	163.6	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD1552P370K4-625AXSP12	142.50	218.8	168.8	189	357.6	143	217	168.2	187.7	352.3	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552P370K4-632AXSP12	135.10	210.2	161.4	181.1	346.5	135.9	208.5	160.8	179.9	341.7	225	32	2"	180	21.1	2"	270		

EAW-VD15S2PI400K9-432AXSP12	109.10	173	131.2	148.3	-	109.6	171.9	131	147.6	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD15S2PI400K9-525AXSP12	130.00	202.3	155	174.2	-	130.5	200.9	154.6	173.2	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI400K9-532AXSP12	121.80	191.3	146	164.4	-	122.6	190.1	145.6	163.6	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI400K9-625AXSP12	142.50	218.8	168.8	189	357.6	143	217	168.2	187.7	352.3	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI400K9-632AXSP12	135.10	210.2	161.4	181.1	346.5	135.9	208.5	160.8	179.9	341.7	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI400R3-425AXSP08	111.50	184.5	138.4	157.7	314.9	114.3	184.5	139.5	157.9	311.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI400R3-432AXSP12	111.20	176.6	134	151.3	-	111.7	175.6	133.6	150.6	-	146	29.2	2"	117	21.7	1-1/2"	176	41	2"
EAW-VD15S2PI400R3-525AXSP12	132.60	206.6	158.2	177.6	-	133.3	205.2	157.7	176.6	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI400R3-532AXSP12	124.40	195.4	149.1	167.6	-	125	194	148.5	166.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI400R3-625AXSP12	145.30	223.2	172.2	192.8	365	146.1	221.5	171.6	191.5	359.8	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI400R3-632AXSP12	137.90	214.6	164.7	184.6	354	138.8	213	164.2	183.5	348.8	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550B3-425AXSP08	122.10	201.7	151.7	172.3	345.6	125.2	201.9	152.7	172.8	342	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550B3-432AXSP08	112.20	187.9	140.1	160	323.4	115.3	188.1	141.4	160.5	320.7	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550B3-525AXSP08	135.40	222.1	167.4	190.3	375.7	139	222.5	168.7	190.8	372.1	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550B3-532AXSP12	135.60	213.7	162.8	183.3	-	136.3	212.4	162.4	182.4	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550B3-625AXSP12	159.20	245.1	188.9	211.4	-	160	243.7	188.4	210.1	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550B3-632AXSP12	151.30	235.3	180.3	202.4	-	152	233.8	179.8	201.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C2-425AXSP08	128.10	211.2	158.5	180.1	362	131.2	211.3	159.7	180.6	358.6	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C2-432AXSP08	117.10	195.7	146.4	166.7	337.7	120.2	195.9	147.6	167.3	334.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C2-525AXSP08	142.70	234.1	176.4	200.1	396.2	146.3	234.2	177.8	200.5	392.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550C2-532AXSP12	141.80	223.8	170.4	192	-	142.5	222.6	169.9	190.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550C2-625AXSP12	168.30	259.8	199.7	223.9	-	168.9	257.9	199.1	222.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C2-632AXSP12	158.90	247.8	189.6	213.2	-	159.7	246.1	189.3	211.7	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C3-425AXSP08	128.10	211.2	158.5	180.1	362	131.2	211.3	159.7	180.6	358.6	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C3-432AXSP08	117.10	195.7	146.4	166.7	337.7	120.2	195.9	147.6	167.3	334.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C3-525AXSP08	142.70	234.1	176.4	200.1	396.2	146.3	234.2	177.8	200.5	392.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550C3-532AXSP12	141.80	223.8	170.4	192	-	142.5	222.6	169.9	190.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550C3-625AXSP12	168.30	259.8	199.7	223.9	-	168.9	257.9	199.1	222.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C3-632AXSP12	158.90	247.8	189.6	213.2	-	159.7	246.1	189.3	211.7	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C4-425AXSP08	128.10	211.2	158.5	180.1	362	131.2	211.3	159.7	180.6	358.6	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C4-432AXSP08	117.10	195.7	146.4	166.7	337.7	120.2	195.9	147.6	167.3	334.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C4-525AXSP08	142.70	234.1	176.4	200.1	396.2	146.3	234.2	177.8	200.5	392.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550C4-532AXSP12	141.80	223.8	170.4	192	-	142.5	222.6	169.9	190.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550C4-625AXSP12	168.30	259.8	199.7	223.9	-	168.9	257.9	199.1	222.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C4-632AXSP12	158.90	247.8	189.6	213.2	-	159.7	246.1	189.3	211.7	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C5-425AXSP08	128.10	211.2	158.5	180.1	362	131.2	211.3	159.7	180.6	358.6	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C5-432AXSP08	117.10	195.7	146.4	166.7	337.7	120.2	195.9	147.6	167.3	334.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C5-525AXSP08	142.70	234.1	176.4	200.1	396.2	146.3	234.2	177.8	200.5	392.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550C5-532AXSP12	141.80	223.8	170.4	192	-	142.5	222.6	169.9	190.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550C5-625AXSP12	168.30	259.8	199.7	223.9	-	168.9	257.9	199.1	222.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C5-632AXSP12	158.90	247.8	189.6	213.2	-	159.7	246.1	189.3	211.7	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C8-425AXSP08	128.10	211.2	158.5	180.1	362	131.2	211.3	159.7	180.6	358.6	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C8-432AXSP08	117.10	195.7	146.4	166.7	337.7	120.2	195.9	147.6	167.3	334.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C8-525AXSP08	142.70	234.1	176.4	200.1	396.2	146.3	234.2	177.8	200.5	392.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550C8-532AXSP12	141.80	223.8	170.4	192	-	142.5	222.6	169.9	190.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550C8-625AXSP12	168.30	259.8	199.7	223.9	-	168.9	257.9	199.1	222.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C8-632AXSP12	158.90	247.8	189.6	213.2	-	159.7	246.1	189.3	211.7	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C9-425AXSP08	128.10	211.2	158.5	180.1	362	131.2	211.3	159.7	180.6	358.6	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C9-432AXSP08	117.10	195.7	146.4	166.7	337.7	120.2	195.9	147.6	167.3	334.8	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550C9-525AXSP08	142.70	234.1	176.4	200.1	396.2	146.3	234.2	177.8	200.5	392.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550C9-532AXSP12	141.80	223.8	170.4	192	-	142.5	222.6	169.9	190.9	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550C9-625AXSP12	168.30	259.8	199.7	223.9	-	168.9	257.9	199.1	222.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550C9-632AXSP12	158.90	247.8	189.6	213.2	-	159.7	246.1	189.3	211.7	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550K2-425AXSP08	122.50	202.4	151.9	172.8	346.2	125.7	202.6	153.2	173	343.1	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550K2-432AXSP08	112.50	188.2	140.5	160.5	324.5	115.5	188.4	141.7	161	321.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550K2-525AXSP08	135.80	223.2	167.9	191	377.1	139.4	223.2	169.3	191.4	373.4	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550K2-532AXSP12	135.80	214.2	163.1	183.9	-	136.7	213.1	162.9	183	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550K2-625AXSP12	160.10	246.7	189.8	212.8	-	160.9	244.7	189.4	211.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550K2-632AXSP12	151.80	236.1	181	203.1	-	152.5	234.6	180.6	202	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD15S2PI550K3-425AXSP08	122.50	202.4	151.9	172.8	346.2	125.7	202.6	153.2	173	343.1	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550K3-432AXSP08	112.50	188.2	140.5	160.5	324.5	115.5	188.4	141.7	161	321.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD15S2PI550K3-525AXSP08	135.80	223.2	167.9	191	377.1	139.4	223.2	169.3	191.4	373.4	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD15S2PI550K3-532AXSP12	135.80	214.2	163.1	183.9	-	136.7	213.1	162.9	183	-	180	30.3	2"	144	20	2"	216	42.5	2"
EAW-VD15S2PI550K3-625AXSP12	160.10	246.7	189.8	212.8	-	160.9	2												

EAW-VD1552PI750C3-425AXSP08	137.60	226.3	169.8	193.3	-	140.9	226.9	171.2	193.8	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C3-432AXSP08	126.00	209.8	156.9	178.7	363.4	129.3	210.3	158.2	179.5	360.2	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C3-525AXSP08	153.10	250.7	189.2	214.6	425.8	157.1	251.2	190.8	215.1	421.7	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C3-532AXSP08	142.30	235.9	176.8	201.4	404	146	236.2	178.3	202.1	400	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C3-625AXSP12	179.50	277.8	213.7	239.4	-	180.7	276.3	213.2	238.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750C4-425AXSP08	137.60	226.3	169.8	193.3	-	140.9	226.9	171.2	193.8	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C4-432AXSP08	126.00	209.8	156.9	178.7	363.4	129.3	210.3	158.2	179.5	360.2	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C4-525AXSP08	153.10	250.7	189.2	214.6	425.8	157.1	251.2	190.8	215.1	421.7	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C4-532AXSP08	142.30	235.9	176.8	201.4	404	146	236.2	178.3	202.1	400	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C4-625AXSP12	179.50	277.8	213.7	239.4	-	180.7	276.3	213.2	238.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750C5-425AXSP08	137.60	226.3	169.8	193.3	-	140.9	226.9	171.2	193.8	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C5-432AXSP08	126.00	209.8	156.9	178.7	363.4	129.3	210.3	158.2	179.5	360.2	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C5-525AXSP08	153.10	250.7	189.2	214.6	425.8	157.1	251.2	190.8	215.1	421.7	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C5-532AXSP08	142.30	235.9	176.8	201.4	404	146	236.2	178.3	202.1	400	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C8-425AXSP08	137.60	226.3	169.8	193.3	-	140.9	226.9	171.2	193.8	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C8-432AXSP08	126.00	209.8	156.9	178.7	363.4	129.3	210.3	158.2	179.5	360.2	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C8-525AXSP08	153.10	250.7	189.2	214.6	425.8	157.1	251.2	190.8	215.1	421.7	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C8-532AXSP08	142.30	235.9	176.8	201.4	404	146	236.2	178.3	202.1	400	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C8-625AXSP12	179.50	277.8	213.7	239.4	-	180.7	276.3	213.2	238.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750C8-632AXSP12	169.90	265.3	203.1	228.3	-	170.8	264	202.6	227.1	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750C9-425AXSP08	137.60	226.3	169.8	193.3	-	140.9	226.9	171.2	193.8	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C9-432AXSP08	126.00	209.8	156.9	178.7	363.4	129.3	210.3	158.2	179.5	360.2	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750C9-525AXSP08	153.10	250.7	189.2	214.6	425.8	157.1	251.2	190.8	215.1	421.7	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C9-532AXSP08	142.30	235.9	176.8	201.4	404	146	236.2	178.3	202.1	400	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750C9-625AXSP12	179.50	277.8	213.7	239.4	-	180.7	276.3	213.2	238.5	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750C9-632AXSP12	169.90	265.3	203.1	228.3	-	170.8	264	202.6	227.1	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-425AXSP08	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-432AXSP08	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-525AXSP08	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-532AXSP08	137.20	228.1	170.7	194.6	389.5	141	228.4	172.4	195.3	386.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-625AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-632AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-632AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-632AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-632AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-632AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	147.70	242	182.4	207	410.5	151.4	242.4	184.1	207.4	406.3	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD1552PI750K2-632AXSP12	173.10	267.4	205.6	230.3	-	174	266	205.2	229.4	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	164.00	256.1	196	220.2	-	165	254.7	195.7	219.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD1552PI750K2-632AXSP12	132.90	218.9	164.3	186.8	375.9	136.1	219.5	165.6	187.4	372.4	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD1552PI750K2-632AXSP12	121.90	203.2	152.1	173.2	351.3	125.2	203.8	153.4	174.1	348.3	225	22.9	2"	180	15.1	2"	270	26.7	


Note: "-" indicates flow rate is outside of unit capability

EAW-VD1552PK370K2-632AXSP16	126.40	195.2	150.2	168.2	-	126.8	193.9	149.7	167.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK370K4-425AXSP12	105.20	168.5	127.6	144.2	-	106.6	168.2	128	144	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK370K4-432AXSP12	97.40	157.1	118.3	134.3	-	98.6	156.8	118.7	134.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK370K4-525AXSP12	116.00	183.8	140	157.9	-	117.5	183.3	140.3	157.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK370K4-532AXSP12	108.40	173.7	131.9	148.9	293.5	110.1	173.3	132.2	148.7	290.1	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK370K4-625AXSP12	126.60	198.7	152.4	171.1	328	128.2	198.1	152.6	170.8	324.3	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK370K4-632AXSP16	126.40	195.2	150.2	168.2	-	126.8	193.9	149.7	167.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK370K5-425AXSP12	105.20	168.5	127.6	144.2	-	106.6	168.2	128	144	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK370K5-432AXSP12	97.40	157.1	118.3	134.3	-	98.6	156.8	118.7	134.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK370K5-525AXSP12	116.00	183.8	140	157.9	-	117.5	183.3	140.3	157.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK370K5-532AXSP12	108.40	173.7	131.9	148.9	293.5	110.1	173.3	132.2	148.7	290.1	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK370K5-625AXSP12	126.60	198.7	152.4	171.1	328	128.2	198.1	152.6	170.8	324.3	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK370K5-632AXSP16	126.40	195.2	150.2	168.2	-	126.8	193.9	149.7	167.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK370K8-425AXSP12	105.20	168.5	127.6	144.2	-	106.6	168.2	128	144	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK370K8-432AXSP12	97.40	157.1	118.3	134.3	-	98.6	156.8	118.7	134.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK370K8-525AXSP12	116.00	183.8	140	157.9	-	117.5	183.3	140.3	157.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK370K8-532AXSP12	108.40	173.7	131.9	148.9	293.5	110.1	173.3	132.2	148.7	290.1	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK370K8-625AXSP12	126.60	198.7	152.4	171.1	328	128.2	198.1	152.6	170.8	324.3	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK370K8-632AXSP16	126.40	195.2	150.2	168.2	-	126.8	193.9	149.7	167.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK400B3-425AXSP12	106.50	170.3	129	145.8	-	107.8	170.2	129.4	145.9	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400B3-432AXSP12	98.60	159	120	136	-	99.9	158.8	120.1	135.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400B3-525AXSP12	117.30	185.7	141.3	159.2	-	118.7	185.2	141.5	159	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400B3-532AXSP12	109.70	175.8	133.2	150.6	296.7	111.3	175.5	133.6	150.4	293.9	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400B3-625AXSP12	127.50	200.2	153.5	172.3	330.4	129.3	199.5	153.7	172	326.7	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400B3-632AXSP16	127.70	197.2	151.7	169.9	-	128	195.9	151.2	169	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK400C3-425AXSP12	109.40	175	132.5	149.9	-	110.7	174.7	132.7	149.7	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400C3-432AXSP12	101.00	163	122.8	139.3	-	102.2	162.8	123.3	139.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400C3-525AXSP12	120.80	191.3	145.7	164.1	-	122.3	191.1	145.8	163.9	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400C3-532AXSP12	113.00	180.8	137	154.7	-	114.3	180.4	137.3	154.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400C3-625AXSP12	132.00	207.2	158.7	178.3	342.8	133.7	206.7	159.1	178	338.9	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400C3-632AXSP12	125.10	199	151.7	170.9	332.2	127.1	198.3	152	170.6	328.4	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400C9-425AXSP12	109.40	175	132.5	149.9	-	110.7	174.7	132.7	149.7	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400C9-432AXSP12	101.00	163	122.8	139.3	-	102.2	162.8	123.3	139.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400C9-525AXSP12	120.80	191.3	145.7	164.1	-	122.3	191.1	145.8	163.9	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400C9-532AXSP12	113.00	180.8	137	154.7	-	114.3	180.4	137.3	154.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400C9-625AXSP12	132.00	207.2	158.7	178.3	342.8	133.7	206.7	159.1	178	338.9	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400C9-632AXSP12	125.10	199	151.7	170.9	332.2	127.1	198.3	152	170.6	328.4	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400K3-425AXSP12	105.20	168.5	127.6	144.2	-	106.6	168.2	128	144	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400K3-432AXSP12	97.40	157.1	118.3	134.3	-	98.6	156.8	118.7	134.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400K3-525AXSP12	116.00	183.8	140	157.9	-	117.5	183.3	140.3	157.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400K3-532AXSP12	108.40	173.7	131.9	148.9	293.5	110.1	173.3	132.2	148.7	290.1	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400K3-625AXSP12	126.60	198.7	152.4	171.1	328	128.2	198.1	152.6	170.8	324.3	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400K3-632AXSP16	126.40	195.2	150.2	168.2	-	126.8	193.9	149.7	167.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK400K9-425AXSP12	105.20	168.5	127.6	144.2	-	106.6	168.2	128	144	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400K9-432AXSP12	97.40	157.1	118.3	134.3	-	98.6	156.8	118.7	134.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400K9-525AXSP12	116.00	183.8	140	157.9	-	117.5	183.3	140.3	157.6	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400K9-532AXSP12	108.40	173.7	131.9	148.9	293.5	110.1	173.3	132.2	148.7	290.1	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400K9-625AXSP12	126.60	198.7	152.4	171.1	328	128.2	198.1	152.6	170.8	324.3	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400K9-632AXSP16	126.40	195.2	150.2	168.2	-	126.8	193.9	149.7	167.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK400R3-425AXSP12	107.20	171.7	129.8	147	-	108.4	171.3	130.2	146.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400R3-432AXSP12	99.20	159.9	120.6	136.7	-	100.5	159.7	121	136.7	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK400R3-525AXSP12	118.20	187.1	142.4	160.6	-	119.8	186.7	142.8	160.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400R3-532AXSP12	110.60	177	134.1	151.6	298.9	112.2	176.7	134.4	151.6	296	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK400R3-625AXSP12	128.90	202.1	154.9	174.2	334.1	130.6	201.6	155.2	173.7	330.4	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK400R3-632AXSP16	128.60	198.7	152.8	171.2	-	129	197.4	152.3	170.3	-	169	33.6	2"	135	25.5	1-1/2"	203	47.2	2"
EAW-VD1552PK508B3-425AXSP12	116.30	186.7	141	159.7	-	117.9	186.5	141.7	159.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK508B3-432AXSP12	107.50	173.7	130.9	148.4	-	108.9	173.8	131.4	148.5	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK508B3-525AXSP12	128.40	203.6	154.9	174.7	-	130	203.4	155.4	174.8	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK508B3-532AXSP12	120.30	192.6	145.8	164.8	-	121.8	192.3	146.2	164.8	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK508B3-625AXSP12	140.30	220.1	168.5	189.4	365	142.3	219.7	169.1	189.3	361.3	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK508B3-632AXSP12	133.30	211.7	161.3	181.9	354.5	135.4	211.3	161.9	181.8	350.9	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK50C2-425AXSP12	121.90	196	148.2	167.7	-	123.5	196	148.6	167.7	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK50C2-432AXSP12	112.30	181.6	136.7	155.2	-	113.8	181.6	137.2	155.2	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK50C2-525AXSP12	135.50	215.5	163.6	184.7	-	137.1	2												

EAW-VD15S2PK550K2-625AXSP12	141.70	222.3	170.2	191.3	368.8	143.5	221.7	170.6	191	364.6	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K2-632AXSP12	134.30	213.3	162.2	182.9	356.7	136.1	212.8	162.7	182.8	353	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K3-425AXSP12	116.90	187.5	141.6	160.3	-	118.3	187.2	142.2	160.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K3-432AXSP12	107.70	174.2	131.2	148.8	-	109.2	174.2	131.7	148.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K3-525AXSP12	129.10	205.1	155.8	175.7	-	130.8	204.8	156.2	175.7	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K3-532AXSP12	120.90	193.5	146.3	165.7	-	122.3	193.1	146.8	165.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K3-625AXSP12	141.70	222.3	170.2	191.3	368.8	143.5	221.7	170.6	191	364.6	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K3-632AXSP12	134.30	213.3	162.2	182.9	356.7	136.1	212.8	162.7	182.8	353	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K4-425AXSP12	116.90	187.5	141.6	160.3	-	118.3	187.2	142.2	160.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K4-432AXSP12	107.70	174.2	131.2	148.8	-	109.2	174.2	131.7	148.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K4-525AXSP12	129.10	205.1	155.8	175.7	-	130.8	204.8	156.2	175.7	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K4-532AXSP12	120.90	193.5	146.3	165.7	-	122.3	193.1	146.8	165.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K4-625AXSP12	141.70	222.3	170.2	191.3	368.8	143.5	221.7	170.6	191	364.6	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K4-632AXSP12	134.30	213.3	162.2	182.9	356.7	136.1	212.8	162.7	182.8	353	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K5-425AXSP12	116.90	187.5	141.6	160.3	-	118.3	187.2	142.2	160.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K5-432AXSP12	107.70	174.2	131.2	148.8	-	109.2	174.2	131.7	148.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K5-525AXSP12	129.10	205.1	155.8	175.7	-	130.8	204.8	156.2	175.7	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K5-532AXSP12	120.90	193.5	146.3	165.7	-	122.3	193.1	146.8	165.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K5-625AXSP12	141.70	222.3	170.2	191.3	368.8	143.5	221.7	170.6	191	364.6	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K5-632AXSP12	134.30	213.3	162.2	182.9	356.7	136.1	212.8	162.7	182.8	353	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K8-425AXSP12	116.90	187.5	141.6	160.3	-	118.3	187.2	142.2	160.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K8-432AXSP12	107.70	174.2	131.2	148.8	-	109.2	174.2	131.7	148.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K8-525AXSP12	129.10	205.1	155.8	175.7	-	130.8	204.8	156.2	175.7	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K8-532AXSP12	120.90	193.5	146.3	165.7	-	122.3	193.1	146.8	165.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K8-625AXSP12	141.70	222.3	170.2	191.3	368.8	143.5	221.7	170.6	191	364.6	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K8-632AXSP12	134.30	213.3	162.2	182.9	356.7	136.1	212.8	162.7	182.8	353	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K9-425AXSP12	116.90	187.5	141.6	160.3	-	118.3	187.2	142.2	160.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K9-432AXSP12	107.70	174.2	131.2	148.8	-	109.2	174.2	131.7	148.8	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550K9-525AXSP12	129.10	205.1	155.8	175.7	-	130.8	204.8	156.2	175.7	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K9-532AXSP12	120.90	193.5	146.3	165.7	-	122.3	193.1	146.8	165.5	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550K9-625AXSP12	141.70	222.3	170.2	191.3	368.8	143.5	221.7	170.6	191	364.6	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550K9-632AXSP12	134.30	213.3	162.2	182.9	356.7	136.1	212.8	162.7	182.8	353	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550R3-425AXSP12	119.80	192.5	145.2	164.5	-	121.3	192.3	145.7	164.6	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550R3-432AXSP12	110.40	178.7	134.5	152.6	-	111.9	178.5	135.1	152.6	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK550R3-525AXSP12	132.40	210.3	152.6	180.3	-	134.1	209.9	160.1	180.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550R3-532AXSP12	123.80	198.2	149.9	169.8	-	125.4	198.3	150.6	169.9	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK550R3-625AXSP12	145.30	228	174.4	196.1	-	147.3	227.5	174.9	195.9	374.7	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK550R3-632AXSP12	137.70	218.4	166.5	187.5	366.1	139.7	218.3	166.8	187.4	362.4	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C2-425AXSP08	118.10	201.7	149.8	171.6	351.9	123	203.4	152.4	173.4	350.1	225	20.3	2"	180	13.3	2"	270	22.9	3"
EAW-VD15S2PK750C2-432AXSP12	119.20	193.5	145.5	165.2	-	121	193.5	146.1	165.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK750C2-525AXSP12	143.60	228.6	173.4	195.9	-	145.5	228.7	174.2	196	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C2-532AXSP12	134.10	215.2	162.7	183.9	-	135.8	215.1	163.4	184.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C2-625AXSP12	158.20	248.4	189.8	213.6	-	160.2	248.2	190.6	213.8	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C2-632AXSP12	149.80	237.9	180.8	203.9	-	152	237.8	181.4	204.1	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C3-425AXSP08	118.10	201.7	149.8	171.6	351.9	123	203.4	152.4	173.4	350.1	225	20.3	2"	180	13.3	2"	270	22.9	3"
EAW-VD15S2PK750C3-432AXSP12	119.20	193.5	145.5	165.2	-	121	193.5	146.1	165.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK750C3-525AXSP12	143.60	228.6	173.4	195.9	-	145.5	228.7	174.2	196	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C3-532AXSP12	134.10	215.2	162.7	183.9	-	135.8	215.1	163.4	184.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C3-625AXSP12	158.20	248.4	189.8	213.6	-	160.2	248.2	190.6	213.8	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C3-632AXSP12	149.80	237.9	180.8	203.9	-	152	237.8	181.4	204.1	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C4-425AXSP08	118.10	201.7	149.8	171.6	351.9	123	203.4	152.4	173.4	350.1	225	20.3	2"	180	13.3	2"	270	22.9	3"
EAW-VD15S2PK750C4-432AXSP12	119.20	193.5	145.5	165.2	-	121	193.5	146.1	165.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK750C4-525AXSP12	143.60	228.6	173.4	195.9	-	145.5	228.7	174.2	196	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C4-532AXSP12	134.10	215.2	162.7	183.9	-	135.8	215.1	163.4	184.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C4-625AXSP12	158.20	248.4	189.8	213.6	-	160.2	248.2	190.6	213.8	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C4-632AXSP12	149.80	237.9	180.8	203.9	-	152	237.8	181.4	204.1	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C5-425AXSP08	118.10	201.7	149.8	171.6	351.9	123	203.4	152.4	173.4	350.1	225	20.3	2"	180	13.3	2"	270	22.9	3"
EAW-VD15S2PK750C5-432AXSP12	119.20	193.5	145.5	165.2	-	121	193.5	146.1	165.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK750C5-525AXSP12	143.60	228.6	173.4	195.9	-	145.5	228.7	174.2	196	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C5-532AXSP12	134.10	215.2	162.7	183.9	-	135.8	215.1	163.4	184.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD15S2PK750C5-625AXSP12	158.20	248.4	189.8	213.6	-	160.2	248.2	190.6	213.8	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C5-632AXSP12	149.80	237.9	180.8	203.9	-	152	237.8	181.4	204.1	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD15S2PK750C8-425AXSP08	118.10	201.7	149.8	171.6	351.9	123	203.4	152.4	173.4	350.1	225	20.3	2"	180	13.3	2"	270	22.9	3"
EAW-VD15S2PK750C8-432AXSP12	119.20	193.5	145.5	165.2	-	121	193.5	146.1	165.3	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD15S2PK750C8-525AXSP12	143.60	228.6	173.4	195.9	-														

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1552PK750K8-532AXSP12	129.70	208	157.2	178	-	131.4	208	157.9	178.3	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK750K8-625AXSP12	152.60	239.5	182.9	205.8	-	154.6	239.1	183.6	205.8	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK750K8-632AXSP12	144.60	229.5	174.6	196.8	-	146.6	229.3	175.2	197	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK750K9-425AXSP08	114.00	195.3	144.8	166	339.9	118.8	196.9	147.2	167.7	338.2	225	20.3	2"	180	13.3	2"	270	22.9	3"
EAW-VD1552PK750K9-432AXSP12	115.70	187.3	140.9	160	-	117.3	187.2	141.6	160.2	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK750K9-525AXSP12	138.60	220.4	167.5	189.1	-	140.5	220.5	168.2	189.2	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK750K9-532AXSP12	129.70	208	157.2	178	-	131.4	208	157.9	178.3	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK750K9-625AXSP12	152.60	239.5	182.9	205.8	-	154.6	239.1	183.6	205.8	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK750K9-632AXSP12	144.60	229.5	174.6	196.8	-	146.6	229.3	175.2	197	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK750R3-425AXSP12	122.80	197.7	149.2	168.8	-	124.5	197.4	149.9	169.1	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK750R3-432AXSP12	113.40	183.7	138.2	156.8	-	114.9	183.7	138.8	156.9	-	146	25.2	2"	117	19.1	1-1/2"	176	35.4	2"
EAW-VD1552PK750R3-525AXSP12	135.70	215.5	163.7	184.7	-	137.6	215.6	164.3	185	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK750R3-532AXSP12	126.90	203.7	153.8	174.1	-	128.8	203.6	154.5	174.3	-	180	26.3	2"	144	17.3	2"	216	36.9	2"
EAW-VD1552PK750R3-625AXSP12	149.20	233.9	178.8	201.1	-	151.1	233.5	179.4	201.1	-	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552PK750R3-632AXSP12	141.30	224.1	170.6	192.3	375.9	143.3	223.9	171.2	192.4	372.4	225	28	2"	180	18.5	2"	270	33.8	3"
EAW-VD1552ZB370C2-425AXSP12	118.50	191.7	145	164.2	325.5	120.5	191.2	145.5	164	321.5	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370C2-432AXSP16	112.70	179	135.8	153.5	-	113.3	177.9	135.5	152.5	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370C2-525AXSP16	135.30	211	161.6	181.5	-	135.9	209.5	161.1	180.4	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C2-532AXSP16	126.60	198.9	151.6	170.8	-	127.2	197.6	151.2	169.9	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C2-625AXSP16	148.90	228.6	176.5	197.4	374.6	149.4	227.1	175.8	196	369	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C2-632AXSP16	141.10	219.2	168.3	188.7	362.3	141.7	217.5	167.5	187.5	356.8	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C4-425AXSP12	118.50	191.7	145	164.2	325.5	120.5	191.2	145.5	164	321.5	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370C4-432AXSP16	112.70	179	135.8	153.5	-	113.3	177.9	135.5	152.5	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370C4-525AXSP16	135.30	211	161.6	181.5	-	135.9	209.5	161.1	180.4	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C4-532AXSP16	126.60	198.9	151.6	170.8	-	127.2	197.6	151.2	169.9	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C4-625AXSP16	148.90	228.6	176.5	197.4	374.6	149.4	227.1	175.8	196	369	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C4-632AXSP16	141.10	219.2	168.3	188.7	362.3	141.7	217.5	167.5	187.5	356.8	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C5-425AXSP12	118.50	191.7	145	164.2	325.5	120.5	191.2	145.5	164	321.5	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370C5-432AXSP16	112.70	179	135.8	153.5	-	113.3	177.9	135.5	152.5	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370C5-525AXSP16	135.30	211	161.6	181.5	-	135.9	209.5	161.1	180.4	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C5-532AXSP16	126.60	198.9	151.6	170.8	-	127.2	197.6	151.2	169.9	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C5-625AXSP16	148.90	228.6	176.5	197.4	374.6	149.4	227.1	175.8	196	369	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C5-632AXSP16	141.10	219.2	168.3	188.7	362.3	141.7	217.5	167.5	187.5	356.8	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C8-425AXSP12	118.50	191.7	145	164.2	325.5	120.5	191.2	145.5	164	321.5	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370C8-432AXSP16	112.70	179	135.8	153.5	-	113.3	177.9	135.5	152.5	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370C8-525AXSP16	135.30	211	161.6	181.5	-	135.9	209.5	161.1	180.4	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C8-532AXSP16	126.60	198.9	151.6	170.8	-	127.2	197.6	151.2	169.9	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370C8-625AXSP16	148.90	228.6	176.5	197.4	374.6	149.4	227.1	175.8	196	369	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C8-632AXSP16	141.10	219.2	168.3	188.7	362.3	141.7	217.5	167.5	187.5	356.8	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370C8-632AXSP12	113.80	184.4	139.4	157.8	312.6	116	184.2	139.9	157.9	308.9	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370K2-432AXSP16	108.90	172.8	131.3	148.1	-	109.6	171.8	131	147.4	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370K2-525AXSP16	130.00	202.4	155.2	174.2	-	130.7	200.9	154.6	173.2	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K2-532AXSP16	121.80	191.2	145.9	164.3	-	122.5	190	145.6	163.5	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K2-625AXSP16	142.60	219	169.2	189.2	358	143.3	217.2	168.3	187.8	352.7	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K2-632AXSP16	135.30	210.3	161.6	181.2	346.8	135.9	208.6	160.9	179.9	341.9	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K4-425AXSP12	113.80	184.4	139.4	157.8	312.6	116	184.2	139.9	157.9	308.9	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370K4-432AXSP16	108.90	172.8	131.3	148.1	-	109.6	171.8	131	147.4	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370K4-525AXSP16	130.00	202.4	155.2	174.2	-	130.7	200.9	154.6	173.2	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K4-532AXSP16	121.80	191.2	145.9	164.3	-	122.5	190	145.6	163.5	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K4-625AXSP16	142.60	219	169.2	189.2	358	143.3	217.2	168.3	187.8	352.7	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K4-632AXSP16	135.30	210.3	161.6	181.2	346.8	135.9	208.6	160.9	179.9	341.9	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K5-425AXSP12	113.80	184.4	139.4	157.8	312.6	116	184.2	139.9	157.9	308.9	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370K5-432AXSP16	108.90	172.8	131.3	148.1	-	109.6	171.8	131	147.4	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370K5-525AXSP16	130.00	202.4	155.2	174.2	-	130.7	200.9	154.6	173.2	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K5-532AXSP16	121.80	191.2	145.9	164.3	-	122.5	190	145.6	163.5	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K5-625AXSP16	142.60	219	169.2	189.2	358	143.3	217.2	168.3	187.8	352.7	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K5-632AXSP16	135.30	210.3	161.6	181.2	346.8	135.9	208.6	160.9	179.9	341.9	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K8-425AXSP12	113.80	184.4	139.4	157.8	312.6	116	184.2	139.9	157.9	308.9	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB370K8-432AXSP16	108.90	172.8	131.3	148.1	-	109.6	171.8	131	147.4	-	146	30.4	2"	117	22.8	1-1/2"	176	42.7	2"
EAW-VD1552ZB370K8-525AXSP16	130.00	202.4	155.2	174.2	-	130.7	200.9	154.6	173.2	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K8-532AXSP16	121.80	191.2	145.9	164.3	-	122.5	190	145.6	163.5	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD1552ZB370K8-625AXSP16	142.60	219	169.2	189.2	358	143.3	217.2	168.3	187.8	352.7	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB370K8-632AXSP16	135.30	210.3	161.6	181.2	346.8	135.9	208.6	160.9	179.9	341.9	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB400R3-425AXSP12	115.50	187	141.3	160															



EAW-VD1552ZB750C5-432AXSP12	131.60	214.7	161.1	183.1	-	133.8	214.7	162.1	183.1	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750C5-525AXSP12	157.80	253.1	191.8	216.8	-	160.6	252.8	192.7	216.9	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750C8-532AXSP12	146.70	237.8	179.6	203.5	404.7	149.2	237.7	180.4	203.4	400.7	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750C5-625AXSP16	179.80	278.3	214	239.8	-	181	276.7	213.5	238.8	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750C5-632AXSP12	161.50	260.7	197.7	223.4	438.9	164.8	260.3	198.7	223.7	433.9	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750C8-425AXSP12	143.00	231.6	174.2	197.7	-	145.4	231.3	175.2	197.8	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750C8-432AXSP12	131.60	214.7	161.1	183.1	-	133.8	214.7	162.1	183.1	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750C8-525AXSP12	157.80	253.1	191.8	216.8	-	160.6	252.8	192.7	216.9	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750C8-532AXSP12	146.70	237.8	179.6	203.5	404.7	149.2	237.7	180.4	203.4	400.7	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750C8-625AXSP16	179.80	278.3	214	239.8	-	181	276.7	213.5	238.8	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750C8-632AXSP12	161.50	260.7	197.7	223.4	438.9	164.8	260.3	198.7	223.7	433.9	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750C9-425AXSP12	143.00	231.6	174.2	197.7	-	145.4	231.3	175.2	197.8	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750C9-432AXSP12	131.60	214.7	161.1	183.1	-	133.8	214.7	162.1	183.1	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750C9-525AXSP12	157.80	253.1	191.8	216.8	-	160.6	252.8	192.7	216.9	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750C9-532AXSP12	146.70	237.8	179.6	203.5	404.7	149.2	237.7	180.4	203.4	400.7	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750C9-625AXSP16	179.80	278.3	214	239.8	-	181	276.7	213.5	238.8	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750C9-632AXSP12	161.50	260.7	197.7	223.4	438.9	164.8	260.3	198.7	223.7	433.9	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K2-425AXSP12	138.50	223.7	168.5	191.1	-	140.7	223.7	169.4	191.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K2-432AXSP12	127.40	207.9	156.2	177.5	-	129.7	208	157	177.6	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K2-532AXSP12	152.10	244.3	185.1	209.1	412	154.7	243.9	185.9	209.4	407.3	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K2-532AXSP12	141.70	230	173.7	196.6	390.8	144.4	229.9	174.5	196.9	386.9	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K2-625AXSP12	165.00	263.1	200.5	226	438.1	168.1	262.5	201.3	225.8	433.3	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K2-632AXSP16	164.10	256.3	196.2	220.4	-	165.1	254.9	195.8	219.5	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750K3-425AXSP12	138.50	223.7	168.5	191.1	-	140.7	223.7	169.4	191.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K3-432AXSP12	127.40	207.9	156.2	177.5	-	129.7	208	157	177.6	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K3-525AXSP12	152.10	244.3	185.1	209.1	412	154.7	243.9	185.9	209.4	407.3	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K3-532AXSP12	141.70	230	173.7	196.6	390.8	144.4	229.9	174.5	196.9	386.9	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K3-625AXSP12	165.00	263.1	200.5	226	438.1	168.1	262.5	201.3	225.8	433.3	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K3-632AXSP16	164.10	256.3	196.2	220.4	-	165.1	254.9	195.8	219.5	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750K4-425AXSP12	138.50	223.7	168.5	191.1	-	140.7	223.7	169.4	191.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K4-432AXSP12	127.40	207.9	156.2	177.5	-	129.7	208	157	177.6	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K4-525AXSP12	152.10	244.3	185.1	209.1	412	154.7	243.9	185.9	209.4	407.3	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K4-532AXSP12	141.70	230	173.7	196.6	390.8	144.4	229.9	174.5	196.9	386.9	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K4-625AXSP12	165.00	263.1	200.5	226	438.1	168.1	262.5	201.3	225.8	433.3	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K4-632AXSP16	164.10	256.3	196.2	220.4	-	165.1	254.9	195.8	219.5	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750K5-425AXSP12	138.50	223.7	168.5	191.1	-	140.7	223.7	169.4	191.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K5-432AXSP12	127.40	207.9	156.2	177.5	-	129.7	208	157	177.6	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K5-525AXSP12	152.10	244.3	185.1	209.1	412	154.7	243.9	185.9	209.4	407.3	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K5-532AXSP12	141.70	230	173.7	196.6	390.8	144.4	229.9	174.5	196.9	386.9	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K5-625AXSP12	165.00	263.1	200.5	226	438.1	168.1	262.5	201.3	225.8	433.3	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K5-632AXSP16	164.10	256.3	196.2	220.4	-	165.1	254.9	195.8	219.5	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750K8-425AXSP12	138.50	223.7	168.5	191.1	-	140.7	223.7	169.4	191.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K8-432AXSP12	127.40	207.9	156.2	177.5	-	129.7	208	157	177.6	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K8-525AXSP12	152.10	244.3	185.1	209.1	412	154.7	243.9	185.9	209.4	407.3	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K8-532AXSP12	141.70	230	173.7	196.6	390.8	144.4	229.9	174.5	196.9	386.9	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K8-625AXSP12	165.00	263.1	200.5	226	438.1	168.1	262.5	201.3	225.8	433.3	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K8-632AXSP16	164.10	256.3	196.2	220.4	-	165.1	254.9	195.8	219.5	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750K9-425AXSP12	138.50	223.7	168.5	191.1	-	140.7	223.7	169.4	191.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K9-432AXSP12	127.40	207.9	156.2	177.5	-	129.7	208	157	177.6	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750K9-525AXSP12	152.10	244.3	185.1	209.1	412	154.7	243.9	185.9	209.4	407.3	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K9-532AXSP12	141.70	230	173.7	196.6	390.8	144.4	229.9	174.5	196.9	386.9	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750K9-625AXSP12	165.00	263.1	200.5	226	438.1	168.1	262.5	201.3	225.8	433.3	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD1552ZB750K9-632AXSP16	164.10	256.3	196.2	220.4	-	165.1	254.9	195.8	219.5	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750R3-425AXSP12	135.60	219.1	165	187	-	137.8	218.8	165.8	187.4	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750R3-432AXSP12	124.70	203.6	153.1	173.9	-	127	203.7	153.9	174	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD1552ZB750R3-525AXSP12	148.80	238.6	180.9	204.6	402.1	151.3	238.2	181.7	204.6	398	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750R3-532AXSP12	138.50	224.9	170	192.4	381.9	141.1	224.8	170.7	192.6	378.1	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD1552ZB750R3-625AXSP16	169.20	261.2	201	225.4	-	170.3	259.9	200.8	224.2	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZB750R3-632AXSP16	160.70	250.3	191.7	215.3	-	161.7	249	191.3	214.4	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD1552ZK017G7-425AXSP08	162.70	277.6	206.2	235.9	484.8	168.9	279.5	209.2	237.7	481.4	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD1552ZK017G7-432AXSP08	147.30	255.3	188.3	216.7	448.5	153.5	257.1	191.3	218.5	445.2	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD1552ZK017G7-525AXSP12	202.80	322.8	244.8	276.7	-	204.8	322.1	245.4	276.1	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK017G7-532AXSP12	187.10	300.8	227.1	257.2	-	189.2	299.6	227.6	256.6	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK017G7-625AXSP12	224.10	352.8	269.5	303.1	-														

EAW-VD1552ZK370K5-425AXSP12	121.80	194.5	147.6	166.8	326.9	123.2	193.4	147.6	166.2	322.7	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK370K5-432AXSP12	112.40	181.5	137.4	155.3	307.7	114	180.7	137.6	154.9	303.9	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK370K5-525AXSP12	133.30	211.2	161.3	181.5	350.9	134.8	210	161.3	180.7	346.2	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK370K5-532AXSP16	129.20	201.1	153.9	173.1	-	129.4	199.3	153.3	171.8	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK370K5-625AXSP16	151.20	229.9	178.2	198.8	373.7	151.2	227.5	177	196.9	367.8	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK370K5-632AXSP16	143.60	220.8	170.1	190.5	362.2	143.6	218.5	169.1	188.7	356.3	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK370K8-425AXSP12	121.80	194.5	147.6	166.8	326.9	123.2	193.4	147.6	166.2	322.7	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK370K8-432AXSP12	112.40	181.5	137.4	155.3	307.7	114	180.7	137.6	154.9	303.9	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK370K8-525AXSP12	133.30	211.2	161.3	181.5	350.9	134.8	210	161.3	180.7	346.2	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK370K8-532AXSP16	129.20	201.1	153.9	173.1	-	129.4	199.3	153.3	171.8	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK370K8-625AXSP16	151.20	229.9	178.2	198.8	373.7	151.2	227.5	177	196.9	367.8	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK370K8-632AXSP16	143.60	220.8	170.1	190.5	362.2	143.6	218.5	169.1	188.7	356.3	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400B3-425AXSP12	123.60	197.1	149.7	169	331.8	125	196.4	149.8	168.6	327.6	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400B3-432AXSP12	114.00	184.1	139.2	157.4	312.1	115.5	183.3	139.2	157	308.3	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400B3-432AXSP12	135.20	214.2	163.6	184.1	356.1	136.9	213.1	163.6	183.3	351.5	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK400B3-532AXSP16	130.80	204.1	156.1	175.3	-	131.2	202.3	155.3	174	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK400B3-625AXSP16	153.20	233.2	180.7	201.6	-	153.3	230.8	179.5	199.7	373.2	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400B3-632AXSP16	145.60	224	172.5	193.2	367.5	145.7	221.7	171.5	191.5	361.7	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400C3-425AXSP12	126.60	201.9	153.3	173	-	127.9	200.8	153.3	172.3	335.3	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400C3-432AXSP12	116.60	188.2	142.2	160.8	318.9	117.9	187.3	142.2	160.4	314.9	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400C3-525AXSP12	138.90	220.1	167.9	189	366.5	140.4	218.8	167.8	188.2	361.1	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK400C3-532AXSP16	134.00	208.9	159.9	179.7	-	134.1	207.2	159	178.2	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK400C3-625AXSP16	157.60	240.3	185.9	207.5	-	157.7	237.8	184.7	205.8	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400C3-632AXSP16	149.40	230.1	177.3	198.4	-	149.6	227.9	176.2	196.8	371.9	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400C9-425AXSP12	126.60	201.9	153.3	173	-	127.9	200.8	153.3	172.3	335.3	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400C9-432AXSP12	116.60	188.2	142.2	160.8	318.9	117.9	187.3	142.2	160.4	314.9	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400C9-525AXSP12	138.90	220.1	167.9	189	366.5	140.4	218.8	167.8	188.2	361.1	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK400C9-532AXSP16	134.00	208.9	159.9	179.7	-	134.1	207.2	159	178.2	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK400C9-625AXSP16	157.60	240.3	185.9	207.5	-	157.7	237.8	184.7	205.8	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400C9-632AXSP16	149.40	230.1	177.3	198.4	-	149.6	227.9	176.2	196.8	371.9	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400K3-425AXSP12	121.80	194.5	147.6	166.8	326.9	123.2	193.4	147.6	166.2	322.7	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400K3-432AXSP12	112.40	181.5	137.4	155.3	307.7	114	180.7	137.6	154.9	303.9	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400K3-525AXSP12	133.30	211.2	161.3	181.5	350.9	134.8	210	161.3	180.7	346.2	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK400K3-532AXSP16	129.20	201.1	153.9	173.1	-	129.4	199.3	153.3	171.8	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK400K3-625AXSP16	151.20	229.9	178.2	198.8	373.7	151.2	227.5	177	196.9	367.8	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400K3-632AXSP16	143.60	220.8	170.1	190.5	362.2	143.6	218.5	169.1	188.7	356.3	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400K9-425AXSP12	121.80	194.5	147.6	166.8	326.9	123.2	193.4	147.6	166.2	322.7	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400K9-432AXSP12	112.40	181.5	137.4	155.3	307.7	114	180.7	137.6	154.9	303.9	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400K9-525AXSP12	133.30	211.2	161.3	181.5	350.9	134.8	210	161.3	180.7	346.2	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK400K9-532AXSP16	129.20	201.1	153.9	173.1	-	129.4	199.3	153.3	171.8	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK400K9-625AXSP16	151.20	229.9	178.2	198.8	373.7	151.2	227.5	177	196.9	367.8	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400K9-632AXSP16	143.60	220.8	170.1	190.5	362.2	143.6	218.5	169.1	188.7	356.3	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400R3-425AXSP12	124.60	198.8	150.7	170.4	334.3	126.1	197.8	150.8	169.8	330.1	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400R3-432AXSP12	114.90	185.6	140.3	158.7	314.9	116.5	184.9	140.4	158.4	310.6	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK400R3-525AXSP12	136.20	215.7	164.7	185.3	359	137.8	214.5	164.7	184.6	354	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK400R3-532AXSP16	131.90	205.5	157.4	176.8	-	132.1	203.7	156.6	175.5	-	180	34.2	2"	144	22.6	2"	216	48	2"
EAW-VD1552ZK400R3-625AXSP16	154.40	234.9	182	203.1	-	154.5	232.6	180.7	201.3	376.1	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK400R3-632AXSP16	146.60	225.5	173.9	194.5	370.5	146.8	223.6	172.9	193	364.7	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550B3-425AXSP12	136.50	217.9	165.2	186.7	-	138.1	217	165.2	186.2	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550B3-432AXSP12	125.70	202.7	153.2	173.5	-	127.3	202.1	153.5	173.1	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550B3-525AXSP12	149.90	237.3	180.9	203.8	396	151.6	236.3	181.1	203	391.2	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550B3-532AXSP12	139.80	223.9	170	191.9	377.1	141.5	222.8	170.2	191.3	372	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550B3-625AXSP12	162.50	254.8	195.6	219.5	420.2	164.3	253.5	195.5	218.7	414.6	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550B3-632AXSP16	161.00	248.2	190.9	214	-	161.2	246.2	190	212.3	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550C2-425AXSP12	142.40	227.6	172.5	194.8	-	143.9	226.6	172.5	194.3	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550C2-432AXSP12	131.10	211.1	159.5	180.5	-	132.4	210.4	159.4	179.9	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550C2-525AXSP12	157.60	249.2	189.7	213.8	-	159.1	248	189.8	213.1	411.1	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550C2-532AXSP12	146.20	234.1	177.7	200.7	394.8	148	233.2	177.9	200	389.8	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550C2-625AXSP12	171.40	269	206.3	231.6	444.7	173.4	267.5	206.1	230.6	438.4	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550C2-632AXSP12	161.40	256.5	195.5	220.5	427.5	163.5	255.1	195.5	219.6	421.8	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550C3-425AXSP12	142.40	227.6	172.5	194.8	-	143.9	226.6	172.5	194.3	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550C3-432AXSP12	131.10	211.1	159.5	180.5	-	132.4	210.4	159.4	179.9	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550C3-525AXSP12	157.60	249.2	189.7	213.8	-	159.1	248	189.8	213.1	411.1</									

EAW-VD1552ZK550K3-632AXSP16	161.30	249	191.5	214.4	-	161.5	246.7	190.4	212.7	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550K4-425AXSP12	137.00	218.3	165.5	187	-	138.4	217.4	165.8	186.6	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K4-432AXSP12	126.20	203.2	153.5	173.9	-	127.8	202.6	153.8	173.5	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K4-525AXSP12	150.40	237.7	181.5	204.2	397.3	152.1	236.7	181.4	203.6	391.9	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K4-532AXSP12	140.00	224.4	170.3	192.3	377.9	142	223.6	170.5	192	373.3	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K4-625AXSP12	163.00	256	196.3	220.6	421.7	165.1	254.6	196.2	219.4	415.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550K4-632AXSP16	161.30	249	191.5	214.4	-	161.5	246.7	190.4	212.7	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550K5-425AXSP12	137.00	218.3	165.5	187	-	138.4	217.4	165.8	186.6	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K5-432AXSP12	126.20	203.2	153.5	173.9	-	127.8	202.6	153.8	173.5	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K5-525AXSP12	150.40	237.7	181.5	204.2	397.3	152.1	236.7	181.4	203.6	391.9	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K5-532AXSP12	140.00	224.4	170.3	192.3	377.9	142	223.6	170.5	192	373.3	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K5-625AXSP12	163.00	256	196.3	220.6	421.7	165.1	254.6	196.2	219.4	415.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550K5-632AXSP16	161.30	249	191.5	214.4	-	161.5	246.7	190.4	212.7	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550K8-425AXSP12	137.00	218.3	165.5	187	-	138.4	217.4	165.8	186.6	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K8-432AXSP12	126.20	203.2	153.5	173.9	-	127.8	202.6	153.8	173.5	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K8-525AXSP12	150.40	237.7	181.5	204.2	397.3	152.1	236.7	181.4	203.6	391.9	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K8-532AXSP12	140.00	224.4	170.3	192.3	377.9	142	223.6	170.5	192	373.3	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K8-625AXSP12	163.00	256	196.3	220.6	421.7	165.1	254.6	196.2	219.4	415.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550K8-632AXSP16	161.30	249	191.5	214.4	-	161.5	246.7	190.4	212.7	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550K9-425AXSP12	137.00	218.3	165.5	187	-	138.4	217.4	165.8	186.6	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K9-432AXSP12	126.20	203.2	153.5	173.9	-	127.8	202.6	153.8	173.5	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550K9-525AXSP12	150.40	237.7	181.5	204.2	397.3	152.1	236.7	181.4	203.6	391.9	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K9-532AXSP12	140.00	224.4	170.3	192.3	377.9	142	223.6	170.5	192	373.3	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550K9-625AXSP12	163.00	256	196.3	220.6	421.7	165.1	254.6	196.2	219.4	415.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550K9-632AXSP16	161.30	249	191.5	214.4	-	161.5	246.7	190.4	212.7	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD1552ZK550R3-425AXSP12	140.70	224.6	170.3	192.3	-	142.2	223.8	170.4	191.9	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550R3-432AXSP12	129.80	208.9	157.9	178.7	-	131.3	208.5	158	178.3	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK550R3-525AXSP12	154.70	244.9	186.5	210.2	409.1	156.6	243.6	186.8	209.4	404.2	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550R3-532AXSP12	144.30	230.8	175.3	198	389.1	146.2	230.1	175.6	197.4	384.5	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK550R3-625AXSP12	168.00	263.7	202.3	227.1	435.1	169.9	262.3	202.2	226.2	429.3	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK550R3-632AXSP12	158.50	252.1	192.3	216.8	420	160.7	250.9	192.4	216.1	414.3	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C2-425AXSP12	153.10	245	185.4	209.7	-	154.9	244.3	185.7	209.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C2-432AXSP12	141.00	227.2	171.3	194.2	-	142.5	226.9	171.7	194	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C2-525AXSP12	169.40	268.1	204.2	230	-	171.4	267.3	204.4	229.7	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C2-532AXSP12	157.70	252.2	190.9	215.9	-	159.6	251.3	191.4	215.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C2-625AXSP12	184.70	289.9	221.9	249.3	479.9	186.9	288.4	222.1	248.6	473.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C2-632AXSP12	174.00	276.3	210.7	237.1	462	176.1	275.2	210.8	236.6	456	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C3-425AXSP12	153.10	245	185.4	209.7	-	154.9	244.3	185.7	209.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C3-432AXSP12	141.00	227.2	171.3	194.2	-	142.5	226.9	171.7	194	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C3-525AXSP12	169.40	268.1	204.2	230	-	171.4	267.3	204.4	229.7	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C3-532AXSP12	157.70	252.2	190.9	215.9	-	159.6	251.3	191.4	215.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C3-625AXSP12	184.70	289.9	221.9	249.3	479.9	186.9	288.4	222.1	248.6	473.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C3-632AXSP12	174.00	276.3	210.7	237.1	462	176.1	275.2	210.8	236.6	456	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C4-425AXSP12	153.10	245	185.4	209.7	-	154.9	244.3	185.7	209.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C4-432AXSP12	141.00	227.2	171.3	194.2	-	142.5	226.9	171.7	194	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C4-525AXSP12	169.40	268.1	204.2	230	-	171.4	267.3	204.4	229.7	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C4-532AXSP12	157.70	252.2	190.9	215.9	-	159.6	251.3	191.4	215.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C4-625AXSP12	184.70	289.9	221.9	249.3	479.9	186.9	288.4	222.1	248.6	473.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C4-632AXSP12	174.00	276.3	210.7	237.1	462	176.1	275.2	210.8	236.6	456	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C5-425AXSP12	153.10	245	185.4	209.7	-	154.9	244.3	185.7	209.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C5-432AXSP12	141.00	227.2	171.3	194.2	-	142.5	226.9	171.7	194	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C5-525AXSP12	169.40	268.1	204.2	230	-	171.4	267.3	204.4	229.7	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C5-532AXSP12	157.70	252.2	190.9	215.9	-	159.6	251.3	191.4	215.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C5-625AXSP12	184.70	289.9	221.9	249.3	479.9	186.9	288.4	222.1	248.6	473.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C5-632AXSP12	174.00	276.3	210.7	237.1	462	176.1	275.2	210.8	236.6	456	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C8-425AXSP12	153.10	245	185.4	209.7	-	154.9	244.3	185.7	209.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C8-432AXSP12	141.00	227.2	171.3	194.2	-	142.5	226.9	171.7	194	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C8-525AXSP12	169.40	268.1	204.2	230	-	171.4	267.3	204.4	229.7	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C8-532AXSP12	157.70	252.2	190.9	215.9	-	159.6	251.3	191.4	215.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD1552ZK750C8-625AXSP12	184.70	289.9	221.9	249.3	479.9	186.9	288.4	222.1	248.6	473.9	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C8-632AXSP12	174.00	276.3	210.7	237.1	462	176.1	275.2	210.8	236.6	456	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750C9-425AXSP12	153.10	245	185.4	209.7	-	154.9	244.3	185.7	209.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C9-432AXSP12	141.00	227.2	171.3	194.2	-	142.5	226.9	171.7	194	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD1552ZK750C9-525AXSP12	169.40	268.1	204.2	230	-	171.4	267.3	204.4	229.7	-									

EAW-VD1552ZK750K9-625AXSP12	177.80	279	213.7	240	461.4	179.8	277.8	213.8	239.3	455.5	304	24.9	3"	244	16.5	3"	365	35	3"	
EAW-VD1552ZK750K9-632AXSP12	167.70	266.7	203.3	229.1	444.9	-	170	265.3	203.4	228.2	439.1	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD1552ZK750R3-425AXSP12	145.30	232	175.7	198.8	-	147	231.4	176	198.2	-	203	27.3	2"	162	18	2"	244	33.6	3"	
EAW-VD1552ZK750R3-432AXSP12	134.10	215.9	162.9	184.5	-	135.7	215.6	163.5	184.2	-	203	27.3	2"	162	18	2"	244	33.6	3"	
EAW-VD1552ZK750R3-525AXSP12	159.90	252.8	192.6	217.1	-	161.7	252	192.7	216.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"	
EAW-VD1553PB370K3-532AXSP12	148.90	238.7	180.8	204.3	402.2	151	237.8	181.2	203.9	397.8	248	24.3	3"	198	19.4	2"	298	34.1	3"	
EAW-VD1553PB370K3-625AXSP12	173.40	272.2	208.7	234.3	450	175.6	271	208.8	233.6	443.7	304	24.9	3"	244	16.5	3"	365	35	3"	
EAW-VD1553PB370K3-632AXSP12	160.80	260.5	198.5	223.9	434.4	166	259.5	198.8	223	428.7	304	24.9	3"	244	16.5	3"	365	35	3"	
EAW-VD1553PB370C2-425AXSP08	154.50	249.9	188.2	213.4	-	157.4	250	189.5	213.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C2-432AXSP08	142.60	232.7	174.7	198.5	-	145.2	233	176	199.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C2-525AXSP08	171.20	274.5	208.2	235.4	462.6	174.3	274.5	209.4	235.8	458.6	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C2-532AXSP08	159.90	259.8	196.4	222.2	441.8	163.2	260.1	197.5	222.8	437.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C2-625AXSP08	182.10	290.5	221.6	249.9	484.4	185.9	290.7	223	250.1	479.9	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C2-632AXSP08	172.90	279.5	211.8	239.6	470.1	176.5	279.4	213.2	239.9	465.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C4-425AXSP08	154.50	249.9	188.2	213.4	-	157.4	250	189.5	213.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C4-432AXSP08	142.60	232.7	174.7	198.5	-	145.2	233	176	199.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C4-525AXSP08	171.20	274.5	208.2	235.4	462.6	174.3	274.5	209.4	235.8	458.6	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C4-532AXSP08	159.90	259.8	196.4	222.2	441.8	163.2	260.1	197.5	222.8	437.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C4-625AXSP08	182.10	290.5	221.6	249.9	484.4	185.9	290.7	223	250.1	479.9	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C4-632AXSP08	172.90	279.5	211.8	239.6	470.1	176.5	279.4	213.2	239.9	465.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C5-425AXSP08	154.50	249.9	188.2	213.4	-	157.4	250	189.5	213.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C5-432AXSP08	142.60	232.7	174.7	198.5	-	145.2	233	176	199.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C5-525AXSP08	171.20	274.5	208.2	235.4	462.6	174.3	274.5	209.4	235.8	458.6	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C5-532AXSP08	159.90	259.8	196.4	222.2	441.8	163.2	260.1	197.5	222.8	437.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C5-625AXSP08	182.10	290.5	221.6	249.9	484.4	185.9	290.7	223	250.1	479.9	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C5-632AXSP08	172.90	279.5	211.8	239.6	470.1	176.5	279.4	213.2	239.9	465.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C8-425AXSP08	154.50	249.9	188.2	213.4	-	157.4	250	189.5	213.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C8-432AXSP08	142.60	232.7	174.7	198.5	-	145.2	233	176	199.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370C8-525AXSP08	171.20	274.5	208.2	235.4	462.6	174.3	274.5	209.4	235.8	458.6	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C8-532AXSP08	159.90	259.8	196.4	222.2	441.8	163.2	260.1	197.5	222.8	437.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370C8-625AXSP08	182.10	290.5	221.6	249.9	484.4	185.9	290.7	223	250.1	479.9	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370C8-632AXSP08	172.90	279.5	211.8	239.6	470.1	176.5	279.4	213.2	239.9	465.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K2-425AXSP08	149.00	240.7	181.3	205.8	-	151.6	240.7	182.4	206.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K2-432AXSP08	137.20	224.6	168.7	191.4	-	139.9	224.4	169.5	192	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K2-525AXSP08	164.50	263.6	200.2	226.3	443.7	167.4	263.9	201.3	226.5	439.8	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K2-532AXSP08	153.90	250.2	188.8	213.9	424.2	156.9	250.3	190.1	214.4	420.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K2-625AXSP08	175.10	279.5	212.9	240.3	465.1	178.7	279.4	214.2	240.2	460.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K2-632AXSP08	166.20	268.6	203.5	230.4	451.2	169.6	268.7	204.7	230.6	446.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K4-425AXSP08	149.00	240.7	181.3	205.8	-	151.6	240.7	182.4	206.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K4-432AXSP08	137.20	224.6	168.7	191.4	-	139.9	224.4	169.5	192	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K4-525AXSP08	164.50	263.6	200.2	226.3	443.7	167.4	263.9	201.3	226.5	439.8	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K4-532AXSP08	153.90	250.2	188.8	213.9	424.2	156.9	250.3	190.1	214.4	420.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K4-625AXSP08	175.10	279.5	212.9	240.3	465.1	178.7	279.4	214.2	240.2	460.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K4-632AXSP08	166.20	268.6	203.5	230.4	451.2	169.6	268.7	204.7	230.6	446.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K5-425AXSP08	149.00	240.7	181.3	205.8	-	151.6	240.7	182.4	206.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K5-432AXSP08	137.20	224.6	168.7	191.4	-	139.9	224.4	169.5	192	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K5-525AXSP08	164.50	263.6	200.2	226.3	443.7	167.4	263.9	201.3	226.5	439.8	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K5-532AXSP08	153.90	250.2	188.8	213.9	424.2	156.9	250.3	190.1	214.4	420.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K5-625AXSP08	175.10	279.5	212.9	240.3	465.1	178.7	279.4	214.2	240.2	460.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K5-632AXSP08	166.20	268.6	203.5	230.4	451.2	169.6	268.7	204.7	230.6	446.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K8-425AXSP08	149.00	240.7	181.3	205.8	-	151.6	240.7	182.4	206.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K8-432AXSP08	137.20	224.6	168.7	191.4	-	139.9	224.4	169.5	192	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB370K8-525AXSP08	164.50	263.6	200.2	226.3	443.7	167.4	263.9	201.3	226.5	439.8	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K8-532AXSP08	153.90	250.2	188.8	213.9	424.2	156.9	250.3	190.1	214.4	420.5	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB370K8-625AXSP08	175.10	279.5	212.9	240.3	465.1	178.7	279.4	214.2	240.2	460.3	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB370K8-632AXSP08	166.20	268.6	203.5	230.4	451.2	169.6	268.7	204.7	230.6	446.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB400B3-425AXSP08	150.40	242.7	183	207.4	-	152.8	243.2	184.3	207.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB400B3-432AXSP08	138.80	226.9	170.5	193.7	-	141.5	227.3	171.6	194.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB400B3-525AXSP08	165.30	265.5	201.3	227.5	447	168.25	265.7	202.6	228	442.9	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB400B3-532AXSP08	155.30	252.2	190.5	215.9	428.4	158.4	252.5	191.9	216.5	424.8	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB400B3-625AXSP08	175.60	279.9	213.5	240.6	465.8	179.3	280.4	214.9	241.4	461.9	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB400B3-632AXSP08	167.00	270.4	204.8	231.7	453.8	171	270.5	206	232.4	450.1	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB400C3-425AXSP08	154.50	249.9	188.2	213.4	-	157.4	250	189.5	213.9	-	22									

EAW-VD1553PB550C2-532AXSP08	179.20	290.8	219	248.4	-	182.9	291	220.7	249.1	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C2-625AXSP08	206.10	328	249.7	281.6	548.8	-	210	328.2	251.1	282.1	544.7	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB550C2-632AXSP08	194.60	313.8	237.8	268.8	529.9	198.6	314.2	239.1	269.5	525.2	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550C3-425AXSP08	172.20	279.3	210.2	238.6	-	175.4	279.8	211.7	239.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550C3-432AXSP08	158.50	259	194.3	220.9	-	161.5	259.8	195.6	221.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550C3-525AXSP08	192.50	308.3	233.4	264.1	-	195.8	308.7	234.8	264.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C3-532AXSP08	179.20	290.8	219	248.4	-	182.9	291	220.7	249.1	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C3-625AXSP08	206.10	328	249.7	281.6	548.8	-	210	328.2	251.1	282.1	544.7	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB550C3-632AXSP08	194.60	313.8	237.8	268.8	529.9	198.6	314.2	239.1	269.5	525.2	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550C4-425AXSP08	172.20	279.3	210.2	238.6	-	175.4	279.8	211.7	239.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550C4-432AXSP08	158.50	259	194.3	220.9	-	161.5	259.8	195.6	221.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550C4-525AXSP08	192.50	308.3	233.4	264.1	-	195.8	308.7	234.8	264.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C4-532AXSP08	179.20	290.8	219	248.4	-	182.9	291	220.7	249.1	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C4-625AXSP08	206.10	328	249.7	281.6	548.8	-	210	328.2	251.1	282.1	544.7	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB550C4-632AXSP08	194.60	313.8	237.8	268.8	529.9	198.6	314.2	239.1	269.5	525.2	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550C9-425AXSP08	172.20	279.3	210.2	238.6	-	175.4	279.8	211.7	239.1	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550C9-432AXSP08	158.50	259	194.3	220.9	-	161.5	259.8	195.6	221.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550C9-525AXSP08	192.50	308.3	233.4	264.1	-	195.8	308.7	234.8	264.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C9-532AXSP08	179.20	290.8	219	248.4	-	182.9	291	220.7	249.1	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550C9-625AXSP08	206.10	328	249.7	281.6	548.8	-	210	328.2	251.1	282.1	544.7	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB550C9-632AXSP08	194.60	313.8	237.8	268.8	529.9	198.6	314.2	239.1	269.5	525.2	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K2-425AXSP08	164.60	266.7	200.9	227.7	-	167.7	267.2	202.2	228.6	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K2-432AXSP08	152.10	248.6	186.4	211.7	-	154.9	248.9	187.6	212.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K2-525AXSP08	183.10	293.4	222.3	251.2	-	186.5	293.7	223.5	251.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K2-532AXSP08	171.00	277.4	209.1	237.3	-	174.4	277.7	210.6	237.9	468.3	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K2-625AXSP08	195.50	311.4	237.1	267.5	520.2	199.4	311.4	238.6	267.9	515.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K2-632AXSP08	185.00	298.4	226.2	255.8	503	189	298.6	227.7	256.4	499	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K3-425AXSP08	164.60	266.7	200.9	227.7	-	167.7	267.2	202.2	228.6	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K3-432AXSP08	152.10	248.6	186.4	211.7	-	154.9	248.9	187.6	212.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K3-525AXSP08	183.10	293.4	222.3	251.2	-	186.5	293.7	223.5	251.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K3-532AXSP08	171.00	277.4	209.1	237.3	-	174.4	277.7	210.6	237.9	468.3	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K3-625AXSP08	195.50	311.4	237.1	267.5	520.2	199.4	311.4	238.6	267.9	515.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K3-632AXSP08	185.00	298.4	226.2	255.8	503	189	298.6	227.7	256.4	499	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K4-425AXSP08	164.60	266.7	200.9	227.7	-	167.7	267.2	202.2	228.6	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K4-432AXSP08	152.10	248.6	186.4	211.7	-	154.9	248.9	187.6	212.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K4-525AXSP08	183.10	293.4	222.3	251.2	-	186.5	293.7	223.5	251.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K4-532AXSP08	171.00	277.4	209.1	237.3	-	174.4	277.7	210.6	237.9	468.3	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K4-625AXSP08	195.50	311.4	237.1	267.5	520.2	199.4	311.4	238.6	267.9	515.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K4-632AXSP08	185.00	298.4	226.2	255.8	503	189	298.6	227.7	256.4	499	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K5-425AXSP08	164.60	266.7	200.9	227.7	-	167.7	267.2	202.2	228.6	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K5-432AXSP08	152.10	248.6	186.4	211.7	-	154.9	248.9	187.6	212.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K5-525AXSP08	183.10	293.4	222.3	251.2	-	186.5	293.7	223.5	251.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K5-532AXSP08	171.00	277.4	209.1	237.3	-	174.4	277.7	210.6	237.9	468.3	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K5-625AXSP08	195.50	311.4	237.1	267.5	520.2	199.4	311.4	238.6	267.9	515.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K5-632AXSP08	185.00	298.4	226.2	255.8	503	189	298.6	227.7	256.4	499	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K8-425AXSP08	164.60	266.7	200.9	227.7	-	167.7	267.2	202.2	228.6	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K8-432AXSP08	152.10	248.6	186.4	211.7	-	154.9	248.9	187.6	212.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K8-525AXSP08	183.10	293.4	222.3	251.2	-	186.5	293.7	223.5	251.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K8-532AXSP08	171.00	277.4	209.1	237.3	-	174.4	277.7	210.6	237.9	468.3	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K8-625AXSP08	195.50	311.4	237.1	267.5	520.2	199.4	311.4	238.6	267.9	515.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K8-632AXSP08	185.00	298.4	226.2	255.8	503	189	298.6	227.7	256.4	499	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K9-425AXSP08	164.60	266.7	200.9	227.7	-	167.7	267.2	202.2	228.6	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K9-432AXSP08	152.10	248.6	186.4	211.7	-	154.9	248.9	187.6	212.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550K9-525AXSP08	183.10	293.4	222.3	251.2	-	186.5	293.7	223.5	251.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K9-532AXSP08	171.00	277.4	209.1	237.3	-	174.4	277.7	210.6	237.9	468.3	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550K9-625AXSP08	195.50	311.4	237.1	267.5	520.2	199.4	311.4	238.6	267.9	515.5	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550K9-632AXSP08	185.00	298.4	226.2	255.8	503	189	298.6	227.7	256.4	499	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550R3-425AXSP08	168.50	273.2	205.5	233.6	-	171.6	273.9	207.1	234.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550R3-432AXSP08	155.70	254.2	190.7	217	-	158.5	254.7	192.1	217.5	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB550R3-525AXSP08	187.60	300.5	227.4	257.2	-	190.9	301	229.2	258	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550R3-532AXSP08	175.10	284.1	214.3	242.9	-	178.8	284.5	215.6	243.7	-	282	21.5	3"	225	18.2	2"	338	30.2	3"	
EAW-VD1553PB550R3-625AXSP08	200.20	319.2	242.9	273.8	533.6	204.3	319.4	244.3	271.3	529	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB550R3-632AXSP08	189.50	305.5	231.8	261.8	515.5	193.6	305.9	233	262.5	511.6	338	22.2	3"	270	14.6	3"	406	31.1	3"	
EAW-VD1553PB750C2-425AXSP08	182.00	296	222.6	252.9	-	185.5	297.2	224.2	253.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"	
EAW-VD1553PB750C2-432AXSP08	167.80																			

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1553PB750C8-525AXSP08	202.90	326.2	246.5	279.1	-	206.7	326.9	248.5	280.1	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750C8-532AXSP08	189.70	307.6	231.5	262.8	-	193.5	308.5	233.3	263.6	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750C8-625AXSP08	217.30	345.8	262.8	296.5	-	221.8	346.8	265	297.8	-	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750C8-632AXSP08	205.60	331.1	250.7	283.6	560.3	210	332.1	252.6	284.5	557	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750C9-425AXSP08	182.00	296	222.6	252.9	-	185.5	297.2	224.2	253.9	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750C9-432AXSP08	167.80	274.8	205.9	234.2	-	171.1	275.8	207.5	235	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750C9-525AXSP08	202.90	326.2	246.5	279.1	-	206.7	326.9	248.5	280.1	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750C9-532AXSP08	189.70	307.6	231.5	262.8	-	193.5	308.5	233.3	263.6	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750C9-625AXSP08	217.30	345.8	262.8	296.5	-	221.8	346.8	265	297.8	-	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750C9-632AXSP08	205.60	331.1	250.7	283.6	560.3	210	332.1	252.6	284.5	557	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K2-425AXSP08	176.10	286.1	215.1	244.3	-	179.4	287.2	217	245.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K2-432AXSP08	162.80	266	199.4	226.9	-	165.9	267	201.1	227.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K2-525AXSP08	196.10	314.5	238	269.3	-	199.8	315.4	239.7	270.5	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K2-532AXSP08	183.60	297.3	224.1	253.8	-	187	298.1	225.8	254.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K2-625AXSP08	209.90	333.9	254	286.5	558.9	214	334.7	256	287.6	555.1	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K2-632AXSP08	198.50	320	242.3	273.9	540.8	202.8	320.7	243.9	275	536.5	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K3-425AXSP08	176.10	286.1	215.1	244.3	-	179.4	287.2	217	245.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K3-432AXSP08	162.80	266	199.4	226.9	-	165.9	267	201.1	227.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K3-525AXSP08	196.10	314.5	238	269.3	-	199.8	315.4	239.7	270.5	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K3-532AXSP08	183.60	297.3	224.1	253.8	-	187	298.1	225.8	254.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K3-625AXSP08	209.90	333.9	254	286.5	558.9	214	334.7	256	287.6	555.1	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K3-632AXSP08	198.50	320	242.3	273.9	540.8	202.8	320.7	243.9	275	536.5	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K4-425AXSP08	176.10	286.1	215.1	244.3	-	179.4	287.2	217	245.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K4-432AXSP08	162.80	266	199.4	226.9	-	165.9	267	201.1	227.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K4-525AXSP08	196.10	314.5	238	269.3	-	199.8	315.4	239.7	270.5	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K4-532AXSP08	183.60	297.3	224.1	253.8	-	187	298.1	225.8	254.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K4-625AXSP08	209.90	333.9	254	286.5	558.9	214	334.7	256	287.6	555.1	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K4-632AXSP08	198.50	320	242.3	273.9	540.8	202.8	320.7	243.9	275	536.5	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K5-425AXSP08	176.10	286.1	215.1	244.3	-	179.4	287.2	217	245.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K5-432AXSP08	162.80	266	199.4	226.9	-	165.9	267	201.1	227.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K5-525AXSP08	196.10	314.5	238	269.3	-	199.8	315.4	239.7	270.5	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K5-532AXSP08	183.60	297.3	224.1	253.8	-	187	298.1	225.8	254.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K5-625AXSP08	209.90	333.9	254	286.5	558.9	214	334.7	256	287.6	555.1	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K5-632AXSP08	198.50	320	242.3	273.9	540.8	202.8	320.7	243.9	275	536.5	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K8-425AXSP08	176.10	286.1	215.1	244.3	-	179.4	287.2	217	245.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K8-432AXSP08	162.80	266	199.4	226.9	-	165.9	267	201.1	227.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K8-525AXSP08	196.10	314.5	238	269.3	-	199.8	315.4	239.7	270.5	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K8-532AXSP08	183.60	297.3	224.1	253.8	-	187	298.1	225.8	254.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K8-625AXSP08	209.90	333.9	254	286.5	558.9	214	334.7	256	287.6	555.1	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K8-632AXSP08	198.50	320	242.3	273.9	540.8	202.8	320.7	243.9	275	536.5	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K9-425AXSP08	176.10	286.1	215.1	244.3	-	179.4	287.2	217	245.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K9-432AXSP08	162.80	266	199.4	226.9	-	165.9	267	201.1	227.8	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750K9-525AXSP08	196.10	314.5	238	269.3	-	199.8	315.4	239.7	270.5	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K9-532AXSP08	183.60	297.3	224.1	253.8	-	187	298.1	225.8	254.9	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750K9-625AXSP08	209.90	333.9	254	286.5	558.9	214	334.7	256	287.6	555.1	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750K9-632AXSP08	198.50	320	242.3	273.9	540.8	202.8	320.7	243.9	275	536.5	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750R3-425AXSP08	172.60	280.2	210.5	238.9	-	175.8	280.6	212.3	240.2	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750R3-432AXSP08	159.40	260.9	195.4	222.3	-	162.6	261.8	197	223.3	-	225	24.9	2"	180	16.4	2"	270	29.4	3"
EAW-VD1553PB750R3-525AXSP08	191.70	307.6	232.9	263.5	-	195.3	308.4	234.6	264.2	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750R3-532AXSP08	179.40	291.1	219.3	248.7	-	183	291.8	220.8	249.7	-	282	21.5	3"	225	18.2	2"	338	30.2	3"
EAW-VD1553PB750R3-625AXSP08	204.60	326.1	247.9	280	545.5	208.9	326.8	249.8	280.6	541.6	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PB750R3-632AXSP08	194.20	313	236.9	268.1	528.5	198.3	313.2	238.8	268.7	524.2	338	22.2	3"	270	14.6	3"	406	31.1	3"
EAW-VD1553PI370C2-425AXSP08	185.40	292.3	222.6	251	-	186.4	290.5	222.1	249.4	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD1553PI370C2-432AXSP08	171.40	272.1	206.7	233.1	-	172.5	270.8	206.2	232	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD1553PI370C2-525AXSP08	207.00	322	246.8	276.9	-	207.9	319.6	245.8	275.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1553PI370C2-532AXSP08	194.00	304.3	232.4	261.6	-	194.8	302.2	231.7	259.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1553PI370C2-625AXSP08	222.60	342.2	263.8	295.1	559.9	223.4	339.5	262.9	293.1	551.7	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1553PI370C2-632AXSP08	210.60	327.8	251.7	282.2	541.7	211.7	325.3	250.6	280.4	533.6	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1553PI370C4-425AXSP08	185.40	292.3	222.6	251	-	186.4	290.5	222.1	249.4	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD1553PI370C4-432AXSP08	171.40	272.1	206.7	233.1	-	172.5	270.8	206.2	232	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD1553PI370C4-525AXSP08	207.00	322	246.8	276.9	-	207.9	319.6	245.8	275.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1553PI370C4-532AXSP08	194.00	304.3	232.4	261.6	-	194.8	302.2	231.7	259.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1553PI370C4-625AXSP08	222.60	342.2	263.8	295.1	559.9	223.4	339.5	262.9	293.1	551.7	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1553PI370C4-632AXSP08	210.60	327.8	251.7	282.2	541.7	211.7	325.3	250.6	280.4	533.6	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1553PI370C5-425AXSP08																			

EAW-VD15S3PI400B3-432AXSP08	167.70	266.2	202	228.3	-	168.7	264.6	201.7	227.2	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400B3-525AXSP08	201.40	312.9	240.1	269.3	-	202.3	310.8	239.2	267.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400B3-532AXSP08	189.20	296.4	226.6	255	-	190.1	294.5	226	253.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400B3-625AXSP08	215.70	331.3	255.6	286.1	541.8	216.6	328.9	254.8	284	534.2	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400B3-632AXSP08	205.00	318.7	244.9	274.5	526.4	206	316.3	243.9	272.8	518.6	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400C3-425AXSP08	185.40	292.3	222.6	251	-	186.4	290.5	222.1	249.4	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400C3-432AXSP08	171.40	272.1	206.7	233.1	-	172.5	270.8	206.2	232	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400C3-525AXSP08	207.00	322	246.8	276.9	-	207.9	319.6	245.8	275.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400C3-532AXSP08	194.00	304.3	232.4	261.6	-	194.8	302.2	231.7	259.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400C3-625AXSP08	222.60	342.2	263.8	295.1	559.9	223.4	339.5	262.9	293.1	551.7	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400C3-632AXSP08	210.60	327.8	251.7	282.2	541.7	211.7	325.3	250.6	280.4	533.6	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400C9-425AXSP08	185.40	292.3	222.6	251	-	186.4	290.5	222.1	249.4	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400C9-432AXSP08	171.40	272.1	206.7	233.1	-	172.5	270.8	206.2	232	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400C9-525AXSP08	207.00	322	246.8	276.9	-	207.9	319.6	245.8	275.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400C9-532AXSP08	194.00	304.3	232.4	261.6	-	194.8	302.2	231.7	259.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400C9-625AXSP08	222.60	342.2	263.8	295.1	559.9	223.4	339.5	262.9	293.1	551.7	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400C9-632AXSP08	210.60	327.8	251.7	282.2	541.7	211.7	325.3	250.6	280.4	533.6	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400K3-425AXSP08	178.60	281.4	214.3	241.5	-	179.6	279.7	213.8	240	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400K3-432AXSP08	165.50	262.5	199.3	225.2	-	166.5	261.3	198.9	224	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400K3-525AXSP08	198.90	308.8	237	265.8	-	199.6	306.5	236	264.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400K3-532AXSP08	186.80	292.8	223.6	251.5	-	187.5	290.8	222.9	249.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400K3-625AXSP08	213.20	327.3	252.9	282.8	535.2	213.9	324.7	251.9	280.8	527.3	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400K3-632AXSP08	202.10	314.4	241.7	270.9	519.2	203.3	312	240.6	269.1	511.4	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400K9-425AXSP08	178.60	281.4	214.3	241.5	-	179.6	279.7	213.8	240	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400K9-432AXSP08	165.50	262.5	199.3	225.2	-	166.5	261.3	198.9	224	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400K9-525AXSP08	198.90	308.8	237	265.8	-	199.6	306.5	236	264.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400K9-532AXSP08	186.80	292.8	223.6	251.5	-	187.5	290.8	222.9	249.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400K9-625AXSP08	213.20	327.3	252.9	282.8	535.2	213.9	324.7	251.9	280.8	527.3	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400K9-632AXSP08	202.10	314.4	241.7	270.9	519.2	203.3	312	240.6	269.1	511.4	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400R3-425AXSP08	182.40	287.2	218.9	246.3	-	183.2	285.6	218.2	245.3	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400R3-432AXSP08	169.00	268	203.3	229.7	-	169.8	266.4	203	228.7	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI400R3-525AXSP08	202.60	314.9	241.5	271.3	-	203.8	312.7	241	269.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400R3-532AXSP08	190.40	298.7	228	256.6	-	191.5	296.9	227.4	255.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI400R3-625AXSP08	217.40	334	257.9	288.4	546.9	218.5	331.4	256.7	286.5	538.4	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI400R3-632AXSP08	206.20	321.1	246.3	276.5	529.7	205.3	318.7	245.7	274.8	522.6	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550B3-425AXSP06	186.10	301.1	227.2	257.5	-	189.3	301	228.2	257.4	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550B3-432AXSP08	183.60	292.3	221.7	250.4	-	185.1	290.9	221.6	249.6	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI550B3-525AXSP08	221.80	345.5	264.6	297.2	-	222.7	343.5	264	295.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550B3-532AXSP08	207.70	326.9	249.1	280.7	-	209	324.8	248.8	279.2	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550B3-625AXSP08	238.10	366.8	282.6	316.3	-	239.4	364.6	281.8	314.8	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550B3-632AXSP08	226.20	352	269.7	302.7	-	227.4	349.8	269.3	301.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C2-425AXSP06	194.90	315.2	237.3	269.2	-	197.8	315	238.3	269.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C2-432AXSP06	178.20	292	219.1	249.1	-	181.5	291.8	220	249	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C2-525AXSP08	233.00	363.9	278.3	312.7	-	234	361.6	277.5	311.2	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C2-532AXSP08	217.30	342.4	260.8	294.1	-	218.6	340.5	260.4	292.4	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C2-625AXSP08	251.80	388.7	299.1	334.9	-	252.6	385.9	297.9	332.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C2-632AXSP08	237.60	370.6	284	318.9	-	238.8	368.2	283.1	317.1	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C3-425AXSP06	194.90	315.2	237.3	269.2	-	197.8	315	238.3	269.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C3-432AXSP06	178.20	292	219.1	249.1	-	181.5	291.8	220	249	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C3-525AXSP08	233.00	363.9	278.3	312.7	-	234	361.6	277.5	311.2	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C3-532AXSP08	217.30	342.4	260.8	294.1	-	218.6	340.5	260.4	292.4	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C3-625AXSP08	251.80	388.7	299.1	334.9	-	252.6	385.9	297.9	332.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C3-632AXSP08	237.60	370.6	284	318.9	-	238.8	368.2	283.1	317.1	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C4-425AXSP06	194.90	315.2	237.3	269.2	-	197.8	315	238.3	269.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C4-432AXSP06	178.20	292	219.1	249.1	-	181.5	291.8	220	249	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C4-525AXSP08	233.00	363.9	278.3	312.7	-	234	361.6	277.5	311.2	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C4-532AXSP08	217.30	342.4	260.8	294.1	-	218.6	340.5	260.4	292.4	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C4-625AXSP08	251.80	388.7	299.1	334.9	-	252.6	385.9	297.9	332.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C4-632AXSP08	237.60	370.6	284	318.9	-	238.8	368.2	283.1	317.1	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C5-425AXSP06	194.90	315.2	237.3	269.2	-	197.8	315	238.3	269.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C5-432AXSP06	178.20	292	219.1	249.1	-	181.5	291.8	220	249	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550C5-525AXSP08	233.00	363.9	278.3	312.7	-	234	361.6	277.5	311.2	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C5-532AXSP08	217.30	342.4	260.8	294.1	-	218.6	340.5	260.4	292.4	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550C5-625AXSP08	251.80	388.7	299.1	334.9	-	252.6	385.9	297.9	332.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550C5-632AXSP08	237.60	370.6	284	3															

EAW-VD15S3PI550K8-425AXSP06	186.30	302.1	227.5	257.9	-	189.5	301.5	228.5	258.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550K8-432AXSP08	184.30	293.3	222.1	250.9	-	185.4	291.9	222	250	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI550K8-525AXSP08	222.50	346.7	265.5	298.2	-	223.7	344.6	264.8	296.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550K8-532AXSP08	208.40	327.6	250	281.2	-	209.7	325.9	249.2	280.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550K8-625AXSP08	239.50	369.1	284.4	318.3	-	240.7	366.6	283.4	316.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550K8-632AXSP08	227.00	353.2	270.6	304.2	-	228.1	350.9	270.2	302.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550K9-425AXSP06	186.30	302.1	227.5	257.9	-	189.5	301.5	228.5	258.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550K9-432AXSP08	184.30	293.3	222.1	250.9	-	185.4	291.9	222	250	-	225	30.9	2"	180	20.4	2"	270	37.8	3"
EAW-VD15S3PI550K9-525AXSP08	222.50	346.7	265.5	298.2	-	223.7	344.6	264.8	296.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550K9-532AXSP08	208.40	327.6	250	281.2	-	209.7	325.9	249.2	280.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550K9-625AXSP08	239.50	369.1	284.4	318.3	-	240.7	366.6	283.4	316.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550K9-632AXSP08	227.00	353.2	270.6	304.2	-	228.1	350.9	270.2	302.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550R3-425AXSP06	191.70	310.3	233.8	265.1	-	194.8	309.8	234.9	265.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550R3-432AXSP06	175.90	288.2	216.4	246	-	179.3	288.2	217.5	246.1	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI550R3-525AXSP08	228.40	356.8	273	306.7	-	229.7	354.7	272.4	305.4	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550R3-532AXSP08	213.80	336.6	256.5	289.2	-	215.2	335	256.3	287.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI550R3-625AXSP08	246.00	379.4	292.1	327.1	-	247.1	377.2	291.3	325.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI550R3-632AXSP08	233.20	363.4	278.2	312.3	-	234.5	361.2	277.5	310.8	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C2-425AXSP06	208.30	337.7	254.2	288.3	-	211.7	338.1	255.4	288.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C2-432AXSP08	191.40	312.9	234.6	266.8	-	194.7	312.6	235.9	267.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C2-525AXSP06	235.40	377.7	286.2	323.4	-	239.3	377.3	287.6	323.7	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750C2-532AXSP08	232.70	367	279.2	315.2	-	234.1	365.5	279.2	313.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750C2-632AXSP08	268.50	416.1	319.6	358.2	-	270.4	413.4	319	356.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C2-632AXSP08	254.00	396.8	303.8	341.4	-	255.8	394.9	303.4	339.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C3-425AXSP06	208.30	337.7	254.2	288.3	-	211.7	338.1	255.4	288.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C3-432AXSP06	191.40	312.9	234.6	266.8	-	194.7	312.6	235.9	267.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C3-525AXSP06	235.40	377.7	286.2	323.4	-	239.3	377.3	287.6	323.7	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750C3-532AXSP08	232.70	367	279.2	315.2	-	234.1	365.5	279.2	313.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750C3-625AXSP08	268.50	416.1	319.6	358.2	-	270.4	413.4	319	356.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C3-632AXSP08	254.00	396.8	303.8	341.4	-	255.8	394.9	303.4	339.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C4-425AXSP06	208.30	337.7	254.2	288.3	-	211.7	338.1	255.4	288.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C4-432AXSP06	191.40	312.9	234.6	266.8	-	194.7	312.6	235.9	267.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C4-525AXSP06	235.40	377.7	286.2	323.4	-	239.3	377.3	287.6	323.7	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750C4-532AXSP08	232.70	367	279.2	315.2	-	234.1	365.5	279.2	313.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750C4-625AXSP08	268.50	416.1	319.6	358.2	-	270.4	413.4	319	356.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C4-632AXSP08	254.00	396.8	303.8	341.4	-	255.8	394.9	303.4	339.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C8-425AXSP06	208.30	337.7	254.2	288.3	-	211.7	338.1	255.4	288.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C8-432AXSP06	191.40	312.9	234.6	266.8	-	194.7	312.6	235.9	267.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750C8-525AXSP06	235.40	377.7	286.2	323.4	-	239.3	377.3	287.6	323.7	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750C8-532AXSP08	232.70	367	279.2	315.2	-	234.1	365.5	279.2	313.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750C8-625AXSP08	268.50	416.1	319.6	358.2	-	270.4	413.4	319	356.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750C8-632AXSP08	254.00	396.8	303.8	341.4	-	255.8	394.9	303.4	339.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K2-425AXSP06	201.40	326.7	246	279.3	-	205	326.6	247.1	279.6	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K2-432AXSP06	185.40	303.1	227.4	258.3	-	188.7	303.4	228.7	259.1	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K2-525AXSP06	227.00	364.6	276.2	312	614.9	230.9	364.1	277.4	312.5	608.7	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750K2-532AXSP08	225.00	354.7	270.2	304.4	-	226.3	353.3	269.8	303.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750K2-625AXSP08	258.80	400	307.6	345	-	260.3	398.1	307.5	343.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K2-632AXSP08	245.20	383	293.1	329.3	-	246.8	381	292.6	328	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K3-425AXSP06	201.40	326.7	246	279.3	-	205	326.6	247.1	279.6	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K3-432AXSP06	185.40	303.1	227.4	258.3	-	188.7	303.4	228.7	259.1	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K3-525AXSP06	227.00	364.6	276.2	312	614.9	230.9	364.1	277.4	312.5	608.7	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750K3-532AXSP08	225.00	354.7	270.2	304.4	-	226.3	353.3	269.8	303.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750K3-625AXSP08	258.80	400	307.6	345	-	260.3	398.1	307.5	343.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K3-632AXSP08	245.20	383	293.1	329.3	-	246.8	381	292.6	328	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K4-425AXSP06	201.40	326.7	246	279.3	-	205	326.6	247.1	279.6	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K4-432AXSP06	185.40	303.1	227.4	258.3	-	188.7	303.4	228.7	259.1	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K4-525AXSP06	227.00	364.6	276.2	312	614.9	230.9	364.1	277.4	312.5	608.7	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750K4-532AXSP08	225.00	354.7	270.2	304.4	-	226.3	353.3	269.8	303.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750K4-625AXSP08	258.80	400	307.6	345	-	260.3	398.1	307.5	343.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K4-632AXSP08	245.20	383	293.1	329.3	-	246.8	381	292.6	328	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD15S3PI750K5-425AXSP06	201.40	326.7	246	279.3	-	205	326.6	247.1	279.6	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K5-432AXSP06	185.40	303.1	227.4	258.3	-	188.7	303.4	228.7	259.1	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD15S3PI750K5-525AXSP06	227.00	364.6	276.2	312	614.9	230.9	364.1	277.4	312.5	608.7	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD15S3PI750K5-532AXSP08	225.00	354.7	270.2	304.4	-	226.3	353.3	269.8	303.1	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD15S3PI750K5-625AXSP08	258.80	400	307.6	345	-	260.3	398.1	307.5	343.2	-	338	28.2	3"						

EAW-VD1553PK370C2-632AXSP08	187.10	297.7	226.9	255.7	497	190	296.7	227.3	255.1	491.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370C4-425AXSP08	166.00	265.9	201	227.6	-	168.2	265.4	201.5	227.2	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370C4-432AXSP08	153.40	247.6	186.5	211.3	-	155.5	247.1	187	211.3	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370C4-525AXSP08	184.90	292.2	222.6	251	-	187.2	291.8	223.2	250.6	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370C4-532AXSP08	172.90	276.6	209.8	237.1	467	175.1	275.9	210.2	236.5	461.6	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370C4-625AXSP08	197.50	310	237.8	267.1	513.5	200	309.2	238	266.3	507.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370C4-632AXSP08	187.10	297.7	226.9	255.7	497	190	296.7	227.3	255.1	491.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370C5-425AXSP08	166.00	265.9	201	227.6	-	168.2	265.4	201.5	227.2	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370C5-432AXSP08	153.40	247.6	186.5	211.3	-	155.5	247.1	187	211.3	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370C5-525AXSP08	184.90	292.2	222.6	251	-	187.2	291.8	223.2	250.6	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370C5-532AXSP08	172.90	276.6	209.8	237.1	467	175.1	275.9	210.2	236.5	461.6	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370C5-625AXSP08	197.50	310	237.8	267.1	513.5	200	309.2	238	266.3	507.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370C5-632AXSP08	187.10	297.7	226.9	255.7	497	190	296.7	227.3	255.1	491.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370C8-425AXSP08	166.00	265.9	201	227.6	-	168.2	265.4	201.5	227.2	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370C8-432AXSP08	153.40	247.6	186.5	211.3	-	155.5	247.1	187	211.3	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370C8-525AXSP08	184.90	292.2	222.6	251	-	187.2	291.8	223.2	250.6	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370C8-532AXSP08	172.90	276.6	209.8	237.1	467	175.1	275.9	210.2	236.5	461.6	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370C8-625AXSP08	197.50	310	237.8	267.1	513.5	200	309.2	238	266.3	507.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370C8-632AXSP08	187.10	297.7	226.9	255.7	497	190	296.7	227.3	255.1	491.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K2-425AXSP08	159.90	255.5	193.8	218.9	-	161.9	255	194.3	218.8	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K2-432AXSP08	148.10	238.5	179.9	203.8	-	150	238	180.4	203.7	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K2-525AXSP08	177.50	280.8	213.9	241.1	469	179.6	279.9	214.3	240.6	463.7	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K2-532AXSP08	166.20	265.8	201.9	228	448.1	168.6	265.4	202.2	227.7	443.5	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K2-625AXSP08	189.40	297.3	227.9	255.9	491.5	191.8	296.4	228.4	255.5	485.3	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K2-632AXSP08	179.70	285.8	217.8	245.6	476.6	182.4	285.1	218.4	245	471.1	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K4-425AXSP08	159.90	255.5	193.8	218.9	-	161.9	255	194.3	218.8	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K4-432AXSP08	148.10	238.5	179.9	203.8	-	150	238	180.4	203.7	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K4-525AXSP08	177.50	280.8	213.9	241.1	469	179.6	279.9	214.3	240.6	463.7	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K4-532AXSP08	166.20	265.8	201.9	228	448.1	168.6	265.4	202.2	227.7	443.5	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K4-625AXSP08	189.40	297.3	227.9	255.9	491.5	191.8	296.4	228.4	255.5	485.3	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K4-632AXSP08	179.70	285.8	217.8	245.6	476.6	182.4	285.1	218.4	245	471.1	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K5-425AXSP08	159.90	255.5	193.8	218.9	-	161.9	255	194.3	218.8	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K5-432AXSP08	148.10	238.5	179.9	203.8	-	150	238	180.4	203.7	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K5-525AXSP08	177.50	280.8	213.9	241.1	469	179.6	279.9	214.3	240.6	463.7	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K5-532AXSP08	166.20	265.8	201.9	228	448.1	168.6	265.4	202.2	227.7	443.5	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K5-625AXSP08	189.40	297.3	227.9	255.9	491.5	191.8	296.4	228.4	255.5	485.3	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K5-632AXSP08	179.70	285.8	217.8	245.6	476.6	182.4	285.1	218.4	245	471.1	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K8-425AXSP08	159.90	255.5	193.8	218.9	-	161.9	255	194.3	218.8	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K8-432AXSP08	148.10	238.5	179.9	203.8	-	150	238	180.4	203.7	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK370K8-525AXSP08	177.50	280.8	213.9	241.1	469	179.6	279.9	214.3	240.6	463.7	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K8-532AXSP08	166.20	265.8	201.9	228	448.1	168.6	265.4	202.2	227.7	443.5	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK370K8-625AXSP08	189.40	297.3	227.9	255.9	491.5	191.8	296.4	228.4	255.5	485.3	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK370K8-632AXSP08	179.70	285.8	217.8	245.6	476.6	182.4	285.1	218.4	245	471.1	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400B3-425AXSP08	161.60	258.8	195.9	221.3	-	163.8	258.1	196.5	221.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400B3-432AXSP08	149.90	241.5	182.1	206.3	-	151.8	241	182.6	206.3	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400B3-525AXSP08	179.20	283.2	216	243.4	-	181.4	282.8	216.5	243.1	468.7	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK400B3-532AXSP08	168.10	269	204	230.4	453.7	170.4	268.5	204.7	230.3	448.7	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK400B3-625AXSP08	190.80	299.5	229.6	257.8	495.1	193.4	298.6	229.9	257.3	489.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400B3-632AXSP08	181.40	288.7	219.9	248	481.5	184.2	287.7	220.6	247.5	476	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400C3-425AXSP08	166.00	265.9	201	227.6	-	168.2	265.4	201.5	227.2	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400C3-432AXSP08	153.40	247.6	186.5	211.3	-	155.5	247.1	187	211.3	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400C3-525AXSP08	184.90	292.2	222.6	251	-	187.2	291.8	223.2	250.6	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK400C3-532AXSP08	172.90	276.6	209.8	237.1	467	175.1	275.9	210.2	236.5	461.6	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK400C3-625AXSP08	197.50	310	237.8	267.1	513.5	200	309.2	238	266.3	507.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400C3-632AXSP08	187.10	297.7	226.9	255.7	497	190	296.7	227.3	255.1	491.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400C9-425AXSP08	166.00	265.9	201	227.6	-	168.2	265.4	201.5	227.2	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400C9-432AXSP08	153.40	247.6	186.5	211.3	-	155.5	247.1	187	211.3	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400C9-525AXSP08	184.90	292.2	222.6	251	-	187.2	291.8	223.2	250.6	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK400C9-532AXSP08	172.90	276.6	209.8	237.1	467	175.1	275.9	210.2	236.5	461.6	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK400C9-625AXSP08	197.50	310	237.8	267.1	513.5	200	309.2	238	266.3	507.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400C9-632AXSP08	187.10	297.7	226.9	255.7	497	190	296.7	227.3	255.1	491.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK400K3-425AXSP08	159.90	255.5	193.8	218.9	-	161.9	255	194.3	218.8	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400K3-432AXSP08	148.10	238.5	179.9	203.8	-	150	238	180.4	203.7	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK400K3-525AXSP08	177.50	280.8	213.9	241.1	469	179.6	279.9	214.3	240.6	463.7	282	23.5	3"						

EAW-VD1553PK550C4-625AXSP08	223.60	350.8	268.1	301.6	-	226.3	349.9	268.7	301.2	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C4-632AXSP08	211.00	335.2	254.8	287.6	562.4	214	334.4	255.6	287.3	556.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C5-425AXSP08	185.20	297.9	224.8	254.7	-	187.7	297.4	225.8	254.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550C5-432AXSP08	170.70	276	207.9	235.7	-	173	275.9	208.7	236	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550C5-525AXSP08	207.40	329.5	250.3	282.3	-	210.1	328.9	250.9	282.2	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550C5-532AXSP08	193.70	310.1	234.8	265.4	-	196.3	309.7	235.2	265.1	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550C5-625AXSP08	223.60	350.8	268.1	301.6	-	226.3	349.9	268.7	301.2	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C5-632AXSP08	211.00	335.2	254.8	287.6	562.4	214	334.4	255.6	287.3	556.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C8-425AXSP08	185.20	297.9	224.8	254.7	-	187.7	297.4	225.8	254.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550C8-432AXSP08	170.70	276	207.9	235.7	-	173	275.9	208.7	236	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550C8-525AXSP08	207.40	329.5	250.3	282.3	-	210.1	328.9	250.9	282.2	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550C8-532AXSP08	193.70	310.1	234.8	265.4	-	196.3	309.7	235.2	265.1	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550C8-625AXSP08	223.60	350.8	268.1	301.6	-	226.3	349.9	268.7	301.2	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C8-632AXSP08	211.00	335.2	254.8	287.6	562.4	214	334.4	255.6	287.3	556.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C9-425AXSP08	185.20	297.9	224.8	254.7	-	187.7	297.4	225.8	254.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550C9-432AXSP08	170.70	276	207.9	235.7	-	173	275.9	208.7	236	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550C9-525AXSP08	207.40	329.5	250.3	282.3	-	210.1	328.9	250.9	282.2	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550C9-532AXSP08	193.70	310.1	234.8	265.4	-	196.3	309.7	235.2	265.1	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550C9-625AXSP08	223.60	350.8	268.1	301.6	-	226.3	349.9	268.7	301.2	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550C9-632AXSP08	211.00	335.2	254.8	287.6	562.4	214	334.4	255.6	287.3	556.4	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K2-425AXSP08	177.40	284.5	215.1	243.5	-	179.8	284.4	216.1	243.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K2-432AXSP08	163.90	264.6	199.4	226.3	-	166.1	264.5	200.3	226.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K2-525AXSP08	197.90	313.4	238.2	268.9	-	200.1	312.9	239.1	268.8	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K2-532AXSP08	185.40	296.4	224.5	253.6	-	187.8	295.5	225.2	253.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K2-625AXSP08	211.90	332.6	254.6	286.2	551.9	214.7	331.7	255.1	285.8	546.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K2-632AXSP08	200.70	319	243	273.6	534.4	203.5	318.3	243.4	273.4	528.8	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K3-425AXSP08	177.40	284.5	215.1	243.5	-	179.8	284.4	216.1	243.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K3-432AXSP08	163.90	264.6	199.4	226.3	-	166.1	264.5	200.3	226.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K3-525AXSP08	197.90	313.4	238.2	268.9	-	200.1	312.9	239.1	268.8	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K3-532AXSP08	185.40	296.4	224.5	253.6	-	187.8	295.5	225.2	253.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K3-625AXSP08	211.90	332.6	254.6	286.2	551.9	214.7	331.7	255.1	285.8	546.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K3-632AXSP08	200.70	319	243	273.6	534.4	203.5	318.3	243.4	273.4	528.8	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K4-425AXSP08	177.40	284.5	215.1	243.5	-	179.8	284.4	216.1	243.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K4-432AXSP08	163.90	264.6	199.4	226.3	-	166.1	264.5	200.3	226.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K4-525AXSP08	197.90	313.4	238.2	268.9	-	200.1	312.9	239.1	268.8	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K4-532AXSP08	185.40	296.4	224.5	253.6	-	187.8	295.5	225.2	253.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K4-625AXSP08	211.90	332.6	254.6	286.2	551.9	214.7	331.7	255.1	285.8	546.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K4-632AXSP08	200.70	319	243	273.6	534.4	203.5	318.3	243.4	273.4	528.8	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K5-425AXSP08	177.40	284.5	215.1	243.5	-	179.8	284.4	216.1	243.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K5-432AXSP08	163.90	264.6	199.4	226.3	-	166.1	264.5	200.3	226.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K5-525AXSP08	197.90	313.4	238.2	268.9	-	200.1	312.9	239.1	268.8	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K5-532AXSP08	185.40	296.4	224.5	253.6	-	187.8	295.5	225.2	253.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K5-625AXSP08	211.90	332.6	254.6	286.2	551.9	214.7	331.7	255.1	285.8	546.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K5-632AXSP08	200.70	319	243	273.6	534.4	203.5	318.3	243.4	273.4	528.8	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K8-425AXSP08	177.40	284.5	215.1	243.5	-	179.8	284.4	216.1	243.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K8-432AXSP08	163.90	264.6	199.4	226.3	-	166.1	264.5	200.3	226.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K8-525AXSP08	197.90	313.4	238.2	268.9	-	200.1	312.9	239.1	268.8	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K8-532AXSP08	185.40	296.4	224.5	253.6	-	187.8	295.5	225.2	253.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K8-625AXSP08	211.90	332.6	254.6	286.2	551.9	214.7	331.7	255.1	285.8	546.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K8-632AXSP08	200.70	319	243	273.6	534.4	203.5	318.3	243.4	273.4	528.8	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K9-425AXSP08	177.40	284.5	215.1	243.5	-	179.8	284.4	216.1	243.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K9-432AXSP08	163.90	264.6	199.4	226.3	-	166.1	264.5	200.3	226.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550K9-525AXSP08	197.90	313.4	238.2	268.9	-	200.1	312.9	239.1	268.8	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K9-532AXSP08	185.40	296.4	224.5	253.6	-	187.8	295.5	225.2	253.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550K9-625AXSP08	211.90	332.6	254.6	286.2	551.9	214.7	331.7	255.1	285.8	546.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550K9-632AXSP08	200.70	319	243	273.6	534.4	203.5	318.3	243.4	273.4	528.8	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550R3-425AXSP08	181.90	292.1	220.6	249.8	-	184.4	291.7	221.3	249.9	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550R3-432AXSP08	167.90	271.6	204.4	232	-	170.2	271.1	205.4	232.1	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK550R3-525AXSP08	202.70	321.1	244.1	275.7	-	205.1	320.7	245.2	275.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550R3-532AXSP08	189.90	303.6	230.1	260	-	192.6	303.5	230.7	259.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK550R3-625AXSP08	217.30	341.1	260.9	293.3	-	220.3	340.7	261.6	293	560.7	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK550R3-632AXSP08	205.90	327.2	248.9	280.8	548.4	208.9	326.6	249.9	280.3	542.9	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750C2-425AXSP06	181.40	301.5	225.2	256.8	-	186.7	303.5	227.7	258.6	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD1553PK750C2-432AXSP08	181.50	294.2	221.1	251.1	-	184.1	294.1	222.2	251.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750C2-525AXSP08	220.10																		

EAW-VD1553PK750K2-532AXSP08	199.10	318.7	241.1	272.6	-	201.9	318.5	242	272.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K2-625AXSP08	228.10	358.3	273.6	308.3	-	231.2	357.8	274.6	307.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K2-632AXSP08	216.20	343.3	261.1	294.3	-	219.2	343	262	294.6	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K3-425AXSP06	175.30	291.9	217.8	248.5	-	180.5	293.8	220.4	250.1	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD1553PK750K3-432AXSP08	175.90	284.7	214.3	243.2	-	178.3	285	215.2	243.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750K3-525AXSP08	212.30	337.1	256.3	289.1	-	215.4	337.1	257.3	289.5	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K3-532AXSP08	199.10	318.7	241.1	272.6	-	201.9	318.5	242	272.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K3-625AXSP08	228.10	358.3	273.6	308.3	-	231.2	357.8	274.6	307.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K3-632AXSP08	216.20	343.3	261.1	294.3	-	219.2	343	262	294.6	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K4-425AXSP06	175.30	291.9	217.8	248.5	-	180.5	293.8	220.4	250.1	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD1553PK750K4-432AXSP08	175.90	284.7	214.3	243.2	-	178.3	285	215.2	243.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750K4-525AXSP08	212.30	337.1	256.3	289.1	-	215.4	337.1	257.3	289.5	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K4-532AXSP08	199.10	318.7	241.1	272.6	-	201.9	318.5	242	272.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K4-625AXSP08	228.10	358.3	273.6	308.3	-	231.2	357.8	274.6	307.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K4-632AXSP08	216.20	343.3	261.1	294.3	-	219.2	343	262	294.6	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K5-425AXSP06	175.30	291.9	217.8	248.5	-	180.5	293.8	220.4	250.1	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD1553PK750K5-432AXSP08	175.90	284.7	214.3	243.2	-	178.3	285	215.2	243.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750K5-525AXSP08	212.30	337.1	256.3	289.1	-	215.4	337.1	257.3	289.5	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K5-532AXSP08	199.10	318.7	241.1	272.6	-	201.9	318.5	242	272.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K5-625AXSP08	228.10	358.3	273.6	308.3	-	231.2	357.8	274.6	307.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K5-632AXSP08	216.20	343.3	261.1	294.3	-	219.2	343	262	294.6	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K8-425AXSP06	175.30	291.9	217.8	248.5	-	180.5	293.8	220.4	250.1	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD1553PK750K8-432AXSP08	175.90	284.7	214.3	243.2	-	178.3	285	215.2	243.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750K8-525AXSP08	212.30	337.1	256.3	289.1	-	215.4	337.1	257.3	289.5	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K8-532AXSP08	199.10	318.7	241.1	272.6	-	201.9	318.5	242	272.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K8-625AXSP08	228.10	358.3	273.6	308.3	-	231.2	357.8	274.6	307.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K8-632AXSP08	216.20	343.3	261.1	294.3	-	219.2	343	262	294.6	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K9-425AXSP06	175.30	291.9	217.8	248.5	-	180.5	293.8	220.4	250.1	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD1553PK750K9-432AXSP08	175.90	284.7	214.3	243.2	-	178.3	285	215.2	243.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750K9-525AXSP08	212.30	337.1	256.3	289.1	-	215.4	337.1	257.3	289.5	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K9-532AXSP08	199.10	318.7	241.1	272.6	-	201.9	318.5	242	272.9	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750K9-625AXSP08	228.10	358.3	273.6	308.3	-	231.2	357.8	274.6	307.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750K9-632AXSP08	216.20	343.3	261.1	294.3	-	219.2	343	262	294.6	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750R3-425AXSP08	186.80	300	226.7	256.4	-	189.3	300.1	227.8	256.9	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750R3-432AXSP08	172.40	279.3	210.1	238.4	-	174.8	279	211	238.6	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD1553PK750R3-525AXSP08	207.80	329.6	250.4	282.8	-	210.5	329.5	251.7	282.7	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750R3-532AXSP08	194.80	312	235.8	267	-	197.5	311.7	237	267.2	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD1553PK750R3-625AXSP08	222.80	349.9	267.5	300.8	-	226	349.4	268.4	300.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553PK750R3-632AXSP08	211.30	335.2	255.2	288	562.4	214.2	334.9	256.3	287.7	557.2	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD1553ZB370C2-425AXSP08	177.10	286.7	216.7	245.5	486.8	180.2	286.4	217.5	245.2	481	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C2-432AXSP08	162.70	266.8	201	227.8	456.1	166	266.5	201.8	228	450.9	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C2-525AXSP08	194.00	312.5	237.3	267.9	524.6	197.7	311.7	238	267.6	517.6	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C2-532AXSP08	180.90	294.8	222.6	252.6	498.9	184.5	294.3	223.5	252.5	492.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C2-625AXSP12	227.70	347.2	268.6	299.9	-	227.7	343.9	266.8	297.4	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370C2-632AXSP12	216.00	332.7	256.1	287	-	216.3	330	254.9	284.7	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370C4-425AXSP08	177.10	286.7	216.7	245.5	486.8	180.2	286.4	217.5	245.2	481	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C4-432AXSP08	162.70	266.8	201	227.8	456.1	166	266.5	201.8	228	450.9	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C4-525AXSP08	194.00	312.5	237.3	267.9	524.6	197.7	311.7	238	267.6	517.6	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C4-532AXSP08	180.90	294.8	222.6	252.6	498.9	184.5	294.3	223.5	252.5	492.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C4-625AXSP12	227.70	347.2	268.6	299.9	-	227.7	343.9	266.8	297.4	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370C4-632AXSP12	216.00	332.7	256.1	287	-	216.3	330	254.9	284.7	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370C5-425AXSP08	177.10	286.7	216.7	245.5	486.8	180.2	286.4	217.5	245.2	481	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C5-432AXSP08	162.70	266.8	201	227.8	456.1	166	266.5	201.8	228	450.9	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C5-525AXSP08	194.00	312.5	237.3	267.9	524.6	197.7	311.7	238	267.6	517.6	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C5-532AXSP08	180.90	294.8	222.6	252.6	498.9	184.5	294.3	223.5	252.5	492.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C5-625AXSP12	227.70	347.2	268.6	299.9	-	227.7	343.9	266.8	297.4	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370C5-632AXSP12	216.00	332.7	256.1	287	-	216.3	330	254.9	284.7	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370C8-425AXSP08	177.10	286.7	216.7	245.5	486.8	180.2	286.4	217.5	245.2	481	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C8-432AXSP08	162.70	266.8	201	227.8	456.1	166	266.5	201.8	228	450.9	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB370C8-525AXSP08	194.00	312.5	237.3	267.9	524.6	197.7	311.7	238	267.6	517.6	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370C8-532AXSP08	180.90	294.8	222.6	252.6	498.9	184.5	294.3	223.5	252.5	492.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370K2-525AXSP08	186.30	299.8	227.3	257.2	502.7	189.7	299	228.3	256.9	496	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB370K2-532AXSP12	188.50	293.6	224.9	252.6	-	188.9	291.1	223.9	250.8	-	248	31.3	3"	198	24	2"	298	43.9	3"
EAW-VD1553ZB370K2-625AXSP12	218.30	332.5	257.1	287	-	218.3	329.3	255.7	284.6	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB370K2-632AXSP12	207.50	319.1	245.9	2															

EAW-VD1553ZB400C9-525AXSP08	194.00	312.5	237.3	267.9	524.6	197.7	311.7	238	267.6	517.6	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB400C9-532AXSP08	180.90	294.8	222.6	252.6	498.9	184.5	294.3	223.5	252.5	492.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB400C9-625AXSP12	227.70	347.2	268.6	299.9	-	227.7	343.9	266.8	297.4	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400C9-632AXSP12	216.00	332.7	256.1	287	-	216.3	330	254.9	284.7	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400K3-425AXSP08	170.10	275.8	208.8	236.4	467.6	173.4	275.5	209.5	236.1	462.1	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB400K3-432AXSP08	156.90	257.5	193.6	220.2	439.6	160.1	257.2	194.8	220	434.6	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB400K3-525AXSP08	186.30	299.8	227.3	257.2	502.7	189.7	299	228.3	256.9	496	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB400K3-532AXSP12	188.50	293.6	224.9	252.6	-	188.9	291.1	223.9	250.8	-	248	31.3	3"	198	24	2"	298	43.9	3"
EAW-VD1553ZB400K3-625AXSP12	218.30	332.5	257.1	287	-	218.3	329.3	255.7	284.6	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400K3-632AXSP12	207.50	319.1	245.9	275.5	-	207.7	316.5	244.7	273.2	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400K9-425AXSP08	170.10	275.8	208.8	236.4	467.6	173.4	275.5	209.5	236.1	462.1	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB400K9-432AXSP08	156.90	257.5	193.6	220.2	439.6	160.1	257.2	194.8	220	434.6	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB400K9-525AXSP08	186.30	299.8	227.3	257.2	502.7	189.7	299	228.3	256.9	496	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB400K9-532AXSP12	188.50	293.6	224.9	252.6	-	188.9	291.1	223.9	250.8	-	248	31.3	3"	198	24	2"	298	43.9	3"
EAW-VD1553ZB400K9-625AXSP12	218.30	332.5	257.1	287	-	218.3	329.3	255.7	284.6	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400K9-632AXSP12	207.50	319.1	245.9	275.5	-	207.7	316.5	244.7	273.2	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400R3-425AXSP08	174.00	281.9	212.9	241.1	477.6	176.8	281.3	213.8	241	472.1	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB400R3-432AXSP08	160.30	262.9	197.8	224.6	449.1	163.6	262.7	198.7	224.5	442.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB400R3-525AXSP08	190.00	306.2	232.3	262.6	513	193.6	305.5	233.1	262.4	506.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB400R3-532AXSP12	192.20	299.6	229.4	257.7	-	192.7	297.3	228.4	256	-	248	31.3	3"	198	24	2"	298	43.9	3"
EAW-VD1553ZB400R3-625AXSP12	222.40	339.3	262.3	293.2	-	222.8	336.2	261	290.4	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB400R3-632AXSP12	211.80	325.9	251	280.9	-	212.1	323	249.6	278.7	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB550B3-425AXSP08	190.60	308.4	232.8	263.6	-	193.6	308	233.6	263.8	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550B3-432AXSP08	175.20	287	215.5	244.7	490.9	178.5	286.7	216.8	244.8	485.9	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550B3-525AXSP08	208.60	335.7	254.7	287.8	564.8	212.6	334.9	255.9	287.5	557.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550B3-532AXSP08	194.80	316.8	239.2	271.3	537.5	198.5	316.3	240.3	271.4	531.7	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550B3-625AXSP08	224.60	358.7	273	308.4	596.5	228.9	358	274.3	308.3	589.5	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550B3-632AXSP12	231.50	357.5	274.7	308.1	-	231.9	354.7	273.8	306	-	304	31.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB550C2-425AXSP08	199.60	322.3	243.2	275.6	-	202.8	321.8	244	275.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C2-432AXSP08	182.90	299	224.9	255	-	186.1	298.7	225.8	255.2	507.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C2-525AXSP08	220.00	353.3	268	302.5	595.3	223.4	352.3	268.7	302.6	588.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C2-532AXSP08	204.20	331.9	250.6	284	563.4	207.6	331.2	251.7	283.9	556.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C2-632AXSP08	237.80	379.6	289.3	326.2	632.2	242.2	378.5	290.4	325.7	624.7	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C3-425AXSP08	223.50	361.6	273.7	310.2	608	228	360.9	274.8	310	600.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C3-432AXSP08	199.60	322.3	243.2	275.6	-	202.8	321.8	244	275.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C3-432AXSP08	182.90	299	224.9	255	-	186.1	298.7	225.8	255.2	507.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C3-525AXSP08	220.00	353.3	268	302.5	595.3	223.4	352.3	268.7	302.6	588.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C3-532AXSP08	204.20	331.9	250.6	284	563.4	207.6	331.2	251.7	283.9	556.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C3-625AXSP08	237.80	379.6	289.3	326.2	632.2	242.2	378.5	290.4	325.7	624.7	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C3-632AXSP08	223.50	361.6	273.7	310.2	608	228	360.9	274.8	310	600.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C4-425AXSP08	199.60	322.3	243.2	275.6	-	202.8	321.8	244	275.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C4-432AXSP08	182.90	299	224.9	255	-	186.1	298.7	225.8	255.2	507.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C4-525AXSP08	220.00	353.3	268	302.5	595.3	223.4	352.3	268.7	302.6	588.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C4-532AXSP08	204.20	331.9	250.6	284	563.4	207.6	331.2	251.7	283.9	556.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C4-625AXSP08	237.80	379.6	289.3	326.2	632.2	242.2	378.5	290.4	325.7	624.7	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C4-632AXSP08	223.50	361.6	273.7	310.2	608	228	360.9	274.8	310	600.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C5-425AXSP08	199.60	322.3	243.2	275.6	-	202.8	321.8	244	275.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C5-432AXSP08	182.90	299	224.9	255	-	186.1	298.7	225.8	255.2	507.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C5-525AXSP08	220.00	353.3	268	302.5	595.3	223.4	352.3	268.7	302.6	588.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C5-532AXSP08	204.20	331.9	250.6	284	563.4	207.6	331.2	251.7	283.9	556.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C5-625AXSP08	237.80	379.6	289.3	326.2	632.2	242.2	378.5	290.4	325.7	624.7	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C5-632AXSP08	223.50	361.6	273.7	310.2	608	228	360.9	274.8	310	600.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C8-425AXSP08	199.60	322.3	243.2	275.6	-	202.8	321.8	244	275.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C8-432AXSP08	182.90	299	224.9	255	-	186.1	298.7	225.8	255.2	507.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C8-525AXSP08	220.00	353.3	268	302.5	595.3	223.4	352.3	268.7	302.6	588.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C8-532AXSP08	204.20	331.9	250.6	284	563.4	207.6	331.2	251.7	283.9	556.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C8-625AXSP08	237.80	379.6	289.3	326.2	632.2	242.2	378.5	290.4	325.7	624.7	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C8-632AXSP08	223.50	361.6	273.7	310.2	608	228	360.9	274.8	310	600.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550C9-425AXSP08	199.60	322.3	243.2	275.6	-	202.8	321.8	244	275.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C9-432AXSP08	182.90	299	224.9	255	-	186.1	298.7	225.8	255.2	507.2	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550C9-525AXSP08	220.00	353.3	268	302.5	595.3	223.4	352.3	268.7	302.6	588.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C9-532AXSP08	204.20	331.9	250.6	284	563.4	207.6	331.2	251.7	283.9	556.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550C9-625AXSP08	237.80	379.6	289.3	326.2	632.2	242.2	378.5	290.4	325.7	624.7	451	24	3"	361	15.8	3"	541	29.9	4

EAW-VD1553ZB550R3-432AXSP08	180.60	295.3	222.2	251.9	506.6	183.9	295.1	223.2	252.3	501.7	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB550R3-525AXSP08	215.30	346.1	262.7	296.9	582.9	219.2	345.8	263.6	296.7	576.5	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550R3-532AXSP08	200.70	326.4	246.6	279.4	553.8	204.6	326.1	247.9	279.6	547.9	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB550R3-625AXSP08	232.20	370.9	282.4	318.8	617.3	236.7	370.2	283.8	318.7	610	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB550R3-632AXSP12	238.80	369.1	283.3	317.9	-	239.2	366.3	282.5	315.8	-	304	21.9	3"	244	21.1	3"	365	44.8	3"
EAW-VD1553ZB750C2-425AXSP08	213.70	346.2	260.9	295.5	-	217.3	345.8	261.9	295.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C2-432AXSP08	196.50	320.8	240.9	273.5	-	199.9	320.9	242.1	274.2	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C2-525AXSP08	235.90	378.5	286.8	324.1	-	240.1	378.2	288.2	324.3	-	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C2-532AXSP08	219.20	355.5	268.5	304.1	605.3	223	355.5	269.7	304.7	599.4	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C2-625AXSP08	255.00	406.6	309.6	348.9	679.1	259.5	406.1	310.9	349	671.3	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C2-632AXSP08	239.90	387.8	293.7	332.1	653.3	244.8	387.1	295.4	332.1	645.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C3-425AXSP08	213.70	346.2	260.9	295.5	-	217.3	345.8	261.9	295.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C3-432AXSP08	196.50	320.8	240.9	273.5	-	199.9	320.9	242.1	274.2	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C3-525AXSP08	235.90	378.5	286.8	324.1	-	240.1	378.2	288.2	324.3	-	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C3-532AXSP08	219.20	355.5	268.5	304.1	605.3	223	355.5	269.7	304.7	599.4	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C3-625AXSP08	255.00	406.6	309.6	348.9	679.1	259.5	406.1	310.9	349	671.3	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C3-632AXSP08	239.90	387.8	293.7	332.1	653.3	244.8	387.1	295.4	332.1	645.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C4-425AXSP08	213.70	346.2	260.9	295.5	-	217.3	345.8	261.9	295.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C4-432AXSP08	196.50	320.8	240.9	273.5	-	199.9	320.9	242.1	274.2	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C4-525AXSP08	235.90	378.5	286.8	324.1	-	240.1	378.2	288.2	324.3	-	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C4-532AXSP08	219.20	355.5	268.5	304.1	605.3	223	355.5	269.7	304.7	599.4	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C4-625AXSP08	255.00	406.6	309.6	348.9	679.1	259.5	406.1	310.9	349	671.3	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C4-632AXSP08	239.90	387.8	293.7	332.1	653.3	244.8	387.1	295.4	332.1	645.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C5-425AXSP08	213.70	346.2	260.9	295.5	-	217.3	345.8	261.9	295.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C5-432AXSP08	196.50	320.8	240.9	273.5	-	199.9	320.9	242.1	274.2	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C5-525AXSP08	235.90	378.5	286.8	324.1	-	240.1	378.2	288.2	324.3	-	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C5-532AXSP08	219.20	355.5	268.5	304.1	605.3	223	355.5	269.7	304.7	599.4	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C5-625AXSP08	255.00	406.6	309.6	348.9	679.1	259.5	406.1	310.9	349	671.3	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C5-632AXSP08	239.90	387.8	293.7	332.1	653.3	244.8	387.1	295.4	332.1	645.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C8-425AXSP08	213.70	346.2	260.9	295.5	-	217.3	345.8	261.9	295.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C8-432AXSP08	196.50	320.8	240.9	273.5	-	199.9	320.9	242.1	274.2	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C8-425AXSP08	235.90	378.5	286.8	324.1	-	240.1	378.2	288.2	324.3	-	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C8-625AXSP08	255.00	406.6	309.6	348.9	679.1	259.5	406.1	310.9	349	671.3	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C8-632AXSP08	239.90	387.8	293.7	332.1	653.3	244.8	387.1	295.4	332.1	645.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C9-425AXSP08	213.70	346.2	260.9	295.5	-	217.3	345.8	261.9	295.7	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C9-432AXSP08	196.50	320.8	240.9	273.5	-	199.9	320.9	242.1	274.2	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750C9-525AXSP08	235.90	378.5	286.8	324.1	-	240.1	378.2	288.2	324.3	-	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C9-532AXSP08	219.20	355.5	268.5	304.1	605.3	223	355.5	269.7	304.7	599.4	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750C9-625AXSP08	255.00	406.6	309.6	348.9	679.1	259.5	406.1	310.9	349	671.3	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750C9-632AXSP08	239.90	387.8	293.7	332.1	653.3	244.8	387.1	295.4	332.1	645.8	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K2-425AXSP08	206.90	334.4	252.4	285.7	-	210.3	334.5	253.3	286.3	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K2-432AXSP08	190.20	310.7	233.5	265.2	-	193.7	310.9	234.5	265.9	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K2-525AXSP08	227.40	365.4	276.8	313.1	616.4	231.4	364.8	278	313.1	610.1	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K2-532AXSP08	211.70	343.8	259.6	293.9	584.6	215.7	343.8	260.8	294.4	578.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K2-625AXSP08	245.30	391	298.1	336.2	652.5	250	390.7	299.5	336	645.4	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K2-632AXSP08	231.30	373.8	283.1	320.4	629.2	235.9	373.6	284.5	320.7	622.5	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K3-425AXSP08	206.90	334.4	252.4	285.7	-	210.3	334.5	253.3	286.3	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K3-432AXSP08	190.20	310.7	233.5	265.2	-	193.7	310.9	234.5	265.9	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K3-525AXSP08	227.40	365.4	276.8	313.1	616.4	231.4	364.8	278	313.1	610.1	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K3-532AXSP08	211.70	343.8	259.6	293.9	584.6	215.7	343.8	260.8	294.4	578.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K3-625AXSP08	245.30	391	298.1	336.2	652.5	250	390.7	299.5	336	645.4	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K3-632AXSP08	231.30	373.8	283.1	320.4	629.2	235.9	373.6	284.5	320.7	622.5	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K4-425AXSP08	206.90	334.4	252.4	285.7	-	210.3	334.5	253.3	286.3	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K4-432AXSP08	190.20	310.7	233.5	265.2	-	193.7	310.9	234.5	265.9	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K4-525AXSP08	227.40	365.4	276.8	313.1	616.4	231.4	364.8	278	313.1	610.1	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K4-532AXSP08	211.70	343.8	259.6	293.9	584.6	215.7	343.8	260.8	294.4	578.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K4-625AXSP08	245.30	391	298.1	336.2	652.5	250	390.7	299.5	336	645.4	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K4-632AXSP08	231.30	373.8	283.1	320.4	629.2	235.9	373.6	284.5	320.7	622.5	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K5-425AXSP08	206.90	334.4	252.4	285.7	-	210.3	334.5	253.3	286.3	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K5-432AXSP08	190.20	310.7	233.5	265.2	-	193.7	310.9	234.5	265.9	-	304	21.9	3"	244	14.4	3"	365	30.7	3"
EAW-VD1553ZB750K5-525AXSP08	227.40	365.4	276.8	313.1	616.4	231.4	364.8	278	313.1	610.1	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K5-532AXSP08	211.70	343.8	259.6	293.9	584.6	215.7	343.8	260.8	294.4	578.8	372	22.7	3"	298	15	3"	446	31.9	3"
EAW-VD1553ZB750K5-625AXSP08	245.30	391	298.1	336.2	652.5	250	390.7	299.5	336	645.4	451	24	3"	361	15.8	3"	541	29.9	4"
EAW-VD1553ZB750K5-632AXSP08	231.30	373.8	283.1	320.4	629.2	235.9	373.6	284.5	320.7	622.5									

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1553ZK370C5-425AXSP08	189.30	302	229.2	258.7	-	191.2	300.3	229.2	258.1	502.3	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370C5-432AXSP08	174.30	281.3	212.5	240.9	477.7	176.2	280.1	212.9	239.8	471	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370C5-525AXSP08	207.70	329.2	251.1	282.7	548.4	210	327.3	251	281.4	540.3	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370C5-532AXSP08	193.40	310.6	235.7	266.2	521.8	196.1	309.1	235.9	265.3	514.8	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370C5-625AXSP08	223.70	352.2	269.7	303.3	579.7	226.6	350	269.6	301.7	570.6	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK370C5-632AXSP12	228.40	349.1	269.7	301.2	-	227.9	345.3	267.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370C8-425AXSP08	189.30	302	229.2	258.7	-	191.2	300.3	229.2	258.1	502.3	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370C8-432AXSP08	174.30	281.3	212.5	240.9	477.7	176.2	280.1	212.9	239.8	471	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370C8-525AXSP08	207.70	329.2	251.1	282.7	548.4	210	327.3	251	281.4	540.3	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370C8-532AXSP08	193.40	310.6	235.7	266.2	521.8	196.1	309.1	235.9	265.3	514.8	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370C8-625AXSP08	223.70	352.2	269.7	303.3	579.7	226.6	350	269.6	301.7	570.6	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK370C8-632AXSP12	228.40	349.1	269.7	301.2	-	227.9	345.3	267.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370K2-425AXSP08	182.10	290.9	220.7	249.5	489.6	184.2	289.3	220.8	248.5	482.7	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K2-432AXSP08	167.90	271.4	205.3	232.6	460.3	170.4	270.2	205.7	232	454.5	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K2-525AXSP08	199.40	315.9	241.3	271.5	525.7	201.6	314.2	241.2	270.3	518.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K2-532AXSP08	186.30	299.1	226.9	256.5	501.8	188.9	297.7	227.1	255.7	494.6	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K2-625AXSP12	230.60	348.5	270.7	301.6	-	230	344.4	268.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370K2-632AXSP12	219.40	335	258.7	289.2	-	219	331.1	256.8	286.1	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370K4-425AXSP08	182.10	290.9	220.7	249.5	489.6	184.2	289.3	220.8	248.5	482.7	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K4-432AXSP08	167.90	271.4	205.3	232.6	460.3	170.4	270.2	205.7	232	454.5	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K4-525AXSP08	199.40	315.9	241.3	271.5	525.7	201.6	314.2	241.2	270.3	518.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K4-532AXSP08	186.30	299.1	226.9	256.5	501.8	188.9	297.7	227.1	255.7	494.6	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K5-425AXSP08	182.10	290.9	220.7	249.5	489.6	184.2	289.3	220.8	248.5	482.7	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K5-432AXSP08	167.90	271.4	205.3	232.6	460.3	170.4	270.2	205.7	232	454.5	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K5-525AXSP08	199.40	315.9	241.3	271.5	525.7	201.6	314.2	241.2	270.3	518.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K5-532AXSP08	186.30	299.1	226.9	256.5	501.8	188.9	297.7	227.1	255.7	494.6	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K5-625AXSP12	230.60	348.5	270.7	301.6	-	230	344.4	268.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370K5-632AXSP12	219.40	335	258.7	289.2	-	219	331.1	256.8	286.1	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370K8-425AXSP08	182.10	290.9	220.7	249.5	489.6	184.2	289.3	220.8	248.5	482.7	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K8-432AXSP08	167.90	271.4	205.3	232.6	460.3	170.4	270.2	205.7	232	454.5	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK370K8-525AXSP08	199.40	315.9	241.3	271.5	525.7	201.6	314.2	241.2	270.3	518.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K8-532AXSP08	186.30	299.1	226.9	256.5	501.8	188.9	297.7	227.1	255.7	494.6	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK370K8-625AXSP12	230.60	348.5	270.7	301.6	-	230	344.4	268.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK370K8-632AXSP12	219.40	335	258.7	289.2	-	219	331.1	256.8	286.1	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK400B3-425AXSP08	184.70	294.8	223.9	252.7	496.4	186.9	293.7	224	252.1	490.2	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400B3-432AXSP08	170.40	275.2	208	235.7	466.9	172.6	274	208.5	234.7	461.1	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400B3-525AXSP08	202.10	320.5	244.7	275.3	533.5	204.7	318.8	244.7	274.3	525.9	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400B3-532AXSP08	188.90	303.5	230.1	260.2	508.8	191.6	301.7	230.4	259.1	502.2	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400B3-625AXSP08	217.30	341.8	261.9	294.8	562.3	220.1	339.7	261.8	293.3	554.2	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK400B3-632AXSP12	222.50	339.9	262.4	293.4	-	222.1	336	260.5	290.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK400C3-425AXSP08	189.30	302	229.2	258.7	-	191.2	300.3	229.2	258.1	502.3	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400C3-432AXSP08	174.30	281.3	212.5	240.9	477.7	176.2	280.1	212.9	239.8	471	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400C3-525AXSP08	207.70	329.2	251.1	282.7	548.4	210	327.3	251	281.4	540.3	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400C3-532AXSP08	193.40	310.6	235.7	266.2	521.8	196.1	309.1	235.9	265.3	514.8	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400C3-625AXSP08	223.70	352.2	269.7	303.3	579.7	226.6	350	269.6	301.7	570.6	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK400C3-632AXSP12	228.40	349.1	269.7	301.2	-	227.9	345.3	267.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK400C9-425AXSP08	189.30	302	229.2	258.7	-	191.2	300.3	229.2	258.1	502.3	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400C9-432AXSP08	174.30	281.3	212.5	240.9	477.7	176.2	280.1	212.9	239.8	471	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400C9-525AXSP08	207.70	329.2	251.1	282.7	548.4	210	327.3	251	281.4	540.3	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400C9-532AXSP08	193.40	310.6	235.7	266.2	521.8	196.1	309.1	235.9	265.3	514.8	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400C9-625AXSP08	223.70	352.2	269.7	303.3	579.7	226.6	350	269.6	301.7	570.6	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK400C9-632AXSP12	228.40	349.1	269.7	301.2	-	227.9	345.3	267.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK400K3-425AXSP08	182.10	290.9	220.7	249.5	489.6	184.2	289.3	220.8	248.5	482.7	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400K3-432AXSP08	167.90	271.4	205.3	232.6	460.3	170.4	270.2	205.7	232	454.5	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400K3-525AXSP08	199.40	315.9	241.3	271.5	525.7	201.6	314.2	241.2	270.3	518.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400K3-532AXSP08	186.30	299.1	226.9	256.5	501.8	188.9	297.7	227.1	255.7	494.6	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400K3-625AXSP12	230.60	348.5	270.7	301.6	-	230	344.4	268.2	298.3	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK400K3-632AXSP12	219.40	335	258.7	289.2	-	219	331.1	256.8	286.1	-	304	34.9	3"	244	23.1	3"	365	48.9	3"
EAW-VD1553ZK400K9-425AXSP08	182.10	290.9	220.7	249.5	489.6	184.2	289.3	220.8	248.5	482.7	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400K9-432AXSP08	167.90	271.4	205.3	232.6	460.3	170.4	270.2	205.7	232	454.5	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK400K9-525AXSP08	199.40	315.9	241.3	271.5	525.7	201.6	314.2	241.2	270.3	518.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400K9-532AXSP08	186.30	299.1	226.9	256.5	501.8	188.9	297.7	227.1	255.7	494.6	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK400K9																			

EAW-VD1553ZK550C5-632AXSP08	239.80	381.6	290.7	327.9	636.6	242.6	379.6	290.7	326.6	628.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550C8-425AXSP08	212.90	340.4	257.9	291.2	-	215	338.9	257.9	290.4	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550C8-432AXSP08	195.80	315.6	238.3	269.8	-	198.2	314.5	238.3	269.4	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550C8-525AXSP08	235.60	372.8	284.1	319.8	-	237.8	371	283.9	318.8	615.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550C8-532AXSP08	218.60	350	265.7	300.1	590.6	221.3	348.8	265.9	299.1	583.2	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550C8-625AXSP08	254.90	400.5	306.9	345.1	662.4	257.9	398.3	307.1	343.2	653.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550C8-632AXSP08	239.80	381.6	290.7	327.9	636.6	242.6	379.6	290.7	326.6	628.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550C9-425AXSP08	212.90	340.4	257.9	291.2	-	215	338.9	257.9	290.4	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550C9-432AXSP08	195.80	315.6	238.3	269.8	-	198.2	314.5	238.3	269.4	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550C9-525AXSP08	235.60	372.8	284.1	319.8	-	237.8	371	283.9	318.8	615.1	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550C9-532AXSP08	218.60	350	265.7	300.1	590.6	221.3	348.8	265.9	299.1	583.2	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550C9-625AXSP08	254.90	400.5	306.9	345.1	662.4	257.9	398.3	307.1	343.2	653.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550C9-632AXSP08	239.80	381.6	290.7	327.9	636.6	242.6	379.6	290.7	326.6	628.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K2-425AXSP08	204.70	326.5	247.4	279.6	-	206.8	325.2	247.8	279	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K2-432AXSP08	188.50	304.3	229.8	260	-	191	303	229.9	259.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K2-525AXSP08	224.90	355.6	271.4	305.8	594.5	227.5	354.1	271.3	304.5	586.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K2-532AXSP08	209.30	335.5	255.1	288	565.3	212.3	334.5	255	287.1	558.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K2-625AXSP08	242.40	381.2	292.1	328.3	629	245.2	379.1	291.9	326.9	620.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K2-632AXSP08	229.00	364.2	277.3	313.1	606.7	232.1	362.4	277.9	312.1	599.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K3-432AXSP08	204.70	326.5	247.4	279.6	-	206.8	325.2	247.8	279	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K3-432AXSP08	188.50	304.3	229.8	260	-	191	303	229.9	259.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K3-525AXSP08	224.90	355.6	271.4	305.8	594.5	227.5	354.1	271.3	304.5	586.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K3-532AXSP08	209.30	335.5	255.1	288	565.3	212.3	334.5	255	287.1	558.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K3-625AXSP08	242.40	381.2	292.1	328.3	629	245.2	379.1	291.9	326.9	620.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K3-632AXSP08	229.00	364.2	277.3	313.1	606.7	232.1	362.4	277.9	312.1	599.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K4-425AXSP08	204.70	326.5	247.4	279.6	-	206.8	325.2	247.8	279	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K4-432AXSP08	188.50	304.3	229.8	260	-	191	303	229.9	259.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K4-525AXSP08	224.90	355.6	271.4	305.8	594.5	227.5	354.1	271.3	304.5	586.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K4-532AXSP08	209.30	335.5	255.1	288	565.3	212.3	334.5	255	287.1	558.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K4-625AXSP08	242.40	381.2	292.1	328.3	629	245.2	379.1	291.9	326.9	620.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K4-632AXSP08	229.00	364.2	277.3	313.1	606.7	232.1	362.4	277.9	312.1	599.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K5-425AXSP08	204.70	326.5	247.4	279.6	-	206.8	325.2	247.8	279	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K5-432AXSP08	188.50	304.3	229.8	260	-	191	303	229.9	259.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K5-525AXSP08	224.90	355.6	271.4	305.8	594.5	227.5	354.1	271.3	304.5	586.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K5-532AXSP08	209.30	335.5	255.1	288	565.3	212.3	334.5	255	287.1	558.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K5-625AXSP08	242.40	381.2	292.1	328.3	629	245.2	379.1	291.9	326.9	620.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K5-632AXSP08	229.00	364.2	277.3	313.1	606.7	232.1	362.4	277.9	312.1	599.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K8-425AXSP08	204.70	326.5	247.4	279.6	-	206.8	325.2	247.8	279	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K8-432AXSP08	188.50	304.3	229.8	260	-	191	303	229.9	259.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K8-525AXSP08	224.90	355.6	271.4	305.8	594.5	227.5	354.1	271.3	304.5	586.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K8-532AXSP08	209.30	335.5	255.1	288	565.3	212.3	334.5	255	287.1	558.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K8-625AXSP08	242.40	381.2	292.1	328.3	629	245.2	379.1	291.9	326.9	620.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K8-632AXSP08	229.00	364.2	277.3	313.1	606.7	232.1	362.4	277.9	312.1	599.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K9-425AXSP08	204.70	326.5	247.4	279.6	-	206.8	325.2	247.8	279	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K9-432AXSP08	188.50	304.3	229.8	260	-	191	303	229.9	259.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550K9-525AXSP08	224.90	355.6	271.4	305.8	594.5	227.5	354.1	271.3	304.5	586.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K9-532AXSP08	209.30	335.5	255.1	288	565.3	212.3	334.5	255	287.1	558.5	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550K9-625AXSP08	242.40	381.2	292.1	328.3	629	245.2	379.1	291.9	326.9	620.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550K9-632AXSP08	229.00	364.2	277.3	313.1	606.7	232.1	362.4	277.9	312.1	599.1	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550R3-425AXSP08	210.20	335.9	254.6	287.5	-	212.5	334.7	254.8	286.9	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550R3-432AXSP08	193.90	312.8	236	267.1	-	196.5	311.7	236.6	267	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK550R3-525AXSP08	231.40	366.4	278.9	314.4	612.9	234.2	365	279.4	313.7	604.8	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550R3-532AXSP08	215.70	345.6	262.1	296	582.8	218.5	344.2	262.5	295.2	575.2	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK550R3-625AXSP08	249.70	392.6	301	337.9	648.2	252.7	390.6	300.9	336.7	639.5	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK550R3-632AXSP08	235.50	375.1	285.8	322.4	625.4	238.9	373.4	286.1	321	616.9	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750C2-425AXSP08	228.80	366.4	277.1	313.9	-	231.6	365.3	277.6	313	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750C2-432AXSP08	210.60	339.6	256	290.3	-	213.2	339.2	257	289.9	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750C2-525AXSP08	253.20	401	305.3	344.5	-	256.2	399.8	305.6	343.5	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750C2-532AXSP08	235.70	377.1	285.9	322.8	-	238.6	375.8	286.1	322.2	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750C2-625AXSP08	274.70	430.9	330	370.9	714.8	277.6	429.3	330.4	369.9	705.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750C2-632AXSP08	258.40	410.9	313.2	352.5	687.8	261.7	409.5	313.3	351.8	678.9	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750C3-425AXSP08	228.80	366.4	277.1	313.9	-	231.6	365.3	277.6	313	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750C3-432AXSP08	210.60	339.6	256	290.3	-	213.2	339.2	257	289.9	-	304	23.8	3"	244	15.8	3"	365	33.5	

EAW-VD1553ZK750K3-625AXSP08	264.40	415.3	317.9	357.2	687.3	267.4	413.5	318.1	356.1	678.5	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K3-632AXSP08	249.20	396.1	302.3	340.1	662.4	252.3	394.7	302.3	339.4	653.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K4-425AXSP08	221.70	354.7	268.3	303.7	-	224.3	353.7	268.7	302.9	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K4-432AXSP08	204.40	329.4	248.7	281.8	-	206.8	329.1	249.2	281.5	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K4-525AXSP08	244.50	387.1	294.6	332.3	-	247.3	385.9	294.9	331.3	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K4-532AXSP08	227.70	364.3	276.5	312.1	615.7	230.6	363.7	276.8	311.5	608.9	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K4-625AXSP08	264.40	415.3	317.9	357.2	687.3	267.4	413.5	318.1	356.1	678.5	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K4-632AXSP08	249.20	396.1	302.3	340.1	662.4	252.3	394.7	302.3	339.4	653.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K5-425AXSP08	221.70	354.7	268.3	303.7	-	224.3	353.7	268.7	302.9	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K5-432AXSP08	204.40	329.4	248.7	281.8	-	206.8	329.1	249.2	281.5	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K5-525AXSP08	244.50	387.1	294.6	332.3	-	247.3	385.9	294.9	331.3	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K5-532AXSP08	227.70	364.3	276.5	312.1	615.7	230.6	363.7	276.8	311.5	608.9	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K5-625AXSP08	264.40	415.3	317.9	357.2	687.3	267.4	413.5	318.1	356.1	678.5	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K5-632AXSP08	249.20	396.1	302.3	340.1	662.4	252.3	394.7	302.3	339.4	653.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K8-425AXSP08	221.70	354.7	268.3	303.7	-	224.3	353.7	268.7	302.9	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K8-432AXSP08	204.40	329.4	248.7	281.8	-	206.8	329.1	249.2	281.5	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K8-525AXSP08	244.50	387.1	294.6	332.3	-	247.3	385.9	294.9	331.3	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K8-532AXSP08	227.70	364.3	276.5	312.1	615.7	230.6	363.7	276.8	311.5	608.9	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K8-625AXSP08	264.40	415.3	317.9	357.2	687.3	267.4	413.5	318.1	356.1	678.5	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K8-632AXSP08	249.20	396.1	302.3	340.1	662.4	252.3	394.7	302.3	339.4	653.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K9-425AXSP08	221.70	354.7	268.3	303.7	-	224.3	353.7	268.7	302.9	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K9-432AXSP08	204.40	329.4	248.7	281.8	-	206.8	329.1	249.2	281.5	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750K9-525AXSP08	244.50	387.1	294.6	332.3	-	247.3	385.9	294.9	331.3	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K9-532AXSP08	227.70	364.3	276.5	312.1	615.7	230.6	363.7	276.8	311.5	608.9	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750K9-625AXSP08	264.40	415.3	317.9	357.2	687.3	267.4	413.5	318.1	356.1	678.5	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750K9-632AXSP08	249.20	396.1	302.3	340.1	662.4	252.3	394.7	302.3	339.4	653.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750R3-425AXSP08	217.10	347	262.6	297.2	-	219.7	346	263	296.4	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750R3-432AXSP08	200.50	322.7	243.4	276.2	-	202.8	322.2	244.3	275.8	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD1553ZK750R3-525AXSP08	239.10	378.1	288	324.7	-	241.8	376.9	288.2	323.8	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750R3-532AXSP08	222.60	356.9	270.7	305.9	602.5	225.8	355.7	270.9	305.3	595	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD1553ZK750R3-625AXSP08	257.80	405.2	310.4	348.7	670.4	261.1	403.5	310.6	347.6	661.8	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1553ZK750R3-632AXSP08	243.30	387.6	295.1	332.9	646.7	246.7	385.6	295.6	331.7	638.4	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD1554PB370C2-425AXSP06	202.00	327.1	246.3	279.6	-	205.5	327.5	248.2	280.3	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C2-432AXSP06	186.20	304.5	228.4	259.5	-	189.8	304.6	229.9	260	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C2-525AXSP06	226.30	363.4	275.3	311	612.8	230.6	363.4	277	311.5	606.8	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB370C2-532AXSP08	225.30	355.1	270.5	304.7	-	226.9	353.7	270.5	303.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB370C2-625AXSP08	256.60	396.4	304.9	341.9	-	258.4	395.1	304.8	340.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C2-632AXSP08	244.40	381.6	292.1	328.2	-	246.3	379.7	292	326.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C4-425AXSP06	202.00	327.1	246.3	279.6	-	205.5	327.5	248.2	280.3	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C4-432AXSP06	186.20	304.5	228.4	259.5	-	189.8	304.6	229.9	260	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C4-525AXSP06	226.30	363.4	275.3	311	612.8	230.6	363.4	277	311.5	606.8	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB370C4-532AXSP08	225.30	355.1	270.5	304.7	-	226.9	353.7	270.5	303.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB370C4-625AXSP08	256.60	396.4	304.9	341.9	-	258.4	395.1	304.8	340.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C4-632AXSP08	244.40	381.6	292.1	328.2	-	246.3	379.7	292	326.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C5-425AXSP06	202.00	327.1	246.3	279.6	-	205.5	327.5	248.2	280.3	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C5-432AXSP06	186.20	304.5	228.4	259.5	-	189.8	304.6	229.9	260	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C5-525AXSP06	226.30	363.4	275.3	311	612.8	230.6	363.4	277	311.5	606.8	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB370C5-532AXSP08	225.30	355.1	270.5	304.7	-	226.9	353.7	270.5	303.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB370C5-625AXSP08	256.60	396.4	304.9	341.9	-	258.4	395.1	304.8	340.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C5-632AXSP08	244.40	381.6	292.1	328.2	-	246.3	379.7	292	326.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C8-425AXSP06	202.00	327.1	246.3	279.6	-	205.5	327.5	248.2	280.3	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C8-432AXSP06	186.20	304.5	228.4	259.5	-	189.8	304.6	229.9	260	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370C8-525AXSP06	226.30	363.4	275.3	311	612.8	230.6	363.4	277	311.5	606.8	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB370C8-532AXSP08	225.30	355.1	270.5	304.7	-	226.9	353.7	270.5	303.9	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB370C8-625AXSP08	256.60	396.4	304.9	341.9	-	258.4	395.1	304.8	340.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370C8-632AXSP08	244.40	381.6	292.1	328.2	-	246.3	379.7	292	326.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370K2-425AXSP06	194.90	315.2	237.3	269.2	-	198	315.3	238.9	269.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370K2-432AXSP06	179.20	293.5	220.4	250.4	-	182.8	294	221.6	250.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370K2-525AXSP08	230.70	360	275.8	309.9	-	232.2	358.7	275.3	308.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB370K2-532AXSP08	217.00	341.9	260.5	293.2	-	218.5	340.4	260.3	292.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB370K2-625AXSP08	247.20	381.3	293.6	328.7	-	248.6	379.1	293.2	327.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370K2-632AXSP08	235.20	366.6	281	315.5	-	236.9	365.1	280.8	314.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB370K4-425AXSP06	194.90	315.2	237.3	269.2	-	198	315.3	238.9	269.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB370K4-432AXSP06	179.20	293.5	220.4	250.4	-	182.8	294	221.6	250										

EAW-VD1554PB400K3-52AXSP08	217.00	341.9	260.5	293.2	-	218.5	340.4	260.3	292.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB400K3-62AXSP08	247.20	381.3	293.6	328.7	-	248.6	379.1	293.2	327.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB400K3-632AXSP08	235.20	366.6	281	315.5	-	236.9	365.1	280.8	314.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB400K9-425AXSP06	194.90	315.2	237.3	269.2	-	198	315.3	238.9	269.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB400K9-432AXSP06	179.20	293.5	220.4	250.4	-	182.8	294	221.6	250.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB400K9-525AXSP08	230.70	360	275.8	309.9	-	232.2	358.7	275.3	308.7	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB400K9-532AXSP08	217.00	341.9	260.5	293.2	-	218.5	340.4	260.3	292.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB400K9-625AXSP08	247.20	381.3	293.6	328.7	-	248.6	379.1	293.2	327.2	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB400K9-632AXSP08	235.20	366.6	281	315.5	-	236.9	365.1	280.8	314.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB400R3-425AXSP06	198.00	320.6	241.2	273.7	-	201.3	320.9	243	274.4	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB400R3-432AXSP06	182.60	298.8	224.2	254.8	-	186.1	299	225.7	255.4	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB400R3-525AXSP08	234.30	366	280.2	314.9	-	235.9	364.8	279.9	313.8	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB400R3-532AXSP08	220.50	347.2	264.7	298.1	-	222.1	346.3	264.7	297.3	-	282	27.5	3"	225	22.1	2"	338	38.6	3"
EAW-VD1554PB400R3-625AXSP08	250.80	387.2	298	334.1	-	252.4	385.7	297.7	332.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB400R3-632AXSP08	239.20	372.5	285.4	320.5	-	240.7	371.2	285.3	319.7	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550R3-425AXSP06	213.90	347.2	261.1	296.7	-	218	348.2	263.1	297.6	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550R3-432AXSP06	197.80	323.2	242.3	275.8	-	201.4	324	244.2	276.6	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550R3-525AXSP06	239.40	384.5	291.2	329.1	-	244.2	384.9	293.2	330.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550R3-532AXSP06	224.20	364.3	274.8	311.5	620.9	228.9	364.8	276.5	312.5	615.7	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550R3-625AXSP08	270.40	418.6	321.5	360.8	-	272.6	417.7	322.2	360.3	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550R3-632AXSP08	258.10	403.6	308.8	347.1	-	260.4	402.4	308.9	346.5	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550C2-425AXSP06	224.90	365.9	274.9	312.2	-	229.1	366.1	277	313	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C2-432AXSP06	207.00	338.7	253.7	288.8	-	210.8	339.3	255.6	289.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C2-525AXSP06	253.90	407.9	308.6	349.3	-	258.4	408.6	310.5	349.9	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C2-625AXSP06	236.60	383.9	289.4	328.3	-	241.1	384.9	291.1	329.2	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C2-632AXSP08	273.90	436.2	331.9	374.4	730.9	279.2	437	333.9	375.1	724.5	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB550C2-632AXSP08	273.50	428.3	327.5	368.4	-	275.8	427.4	327.5	367.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550C3-425AXSP06	224.90	365.9	274.9	312.2	-	229.1	366.1	277	313	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C3-432AXSP06	207.00	338.7	253.7	288.8	-	210.8	339.3	255.6	289.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C3-525AXSP06	253.90	407.9	308.6	349.3	-	258.4	408.6	310.5	349.9	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C3-532AXSP06	236.60	383.9	289.4	328.3	-	241.1	384.9	291.1	329.2	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C3-625AXSP06	273.90	436.2	331.9	374.4	730.9	279.2	437	333.9	375.1	724.5	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB550C3-632AXSP08	273.50	428.3	327.5	368.4	-	275.8	427.4	327.5	367.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550C4-425AXSP06	224.90	365.9	274.9	312.2	-	229.1	366.1	277	313	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C4-432AXSP06	207.00	338.7	253.7	288.8	-	210.8	339.3	255.6	289.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C4-525AXSP06	253.90	407.9	308.6	349.3	-	258.4	408.6	310.5	349.9	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C4-625AXSP06	273.90	436.2	331.9	374.4	730.9	279.2	437	333.9	375.1	724.5	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB550C4-632AXSP08	273.50	428.3	327.5	368.4	-	275.8	427.4	327.5	367.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550C5-425AXSP06	224.90	365.9	274.9	312.2	-	229.1	366.1	277	313	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C5-432AXSP06	207.00	338.7	253.7	288.8	-	210.8	339.3	255.6	289.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C5-525AXSP06	253.90	407.9	308.6	349.3	-	258.4	408.6	310.5	349.9	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C5-532AXSP06	236.60	383.9	289.4	328.3	-	241.1	384.9	291.1	329.2	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C5-625AXSP06	273.90	436.2	331.9	374.4	730.9	279.2	437	333.9	375.1	724.5	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB550C5-632AXSP08	273.50	428.3	327.5	368.4	-	275.8	427.4	327.5	367.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550C8-425AXSP06	224.90	365.9	274.9	312.2	-	229.1	366.1	277	313	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C8-432AXSP06	207.00	338.7	253.7	288.8	-	210.8	339.3	255.6	289.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C8-525AXSP06	253.90	407.9	308.6	349.3	-	258.4	408.6	310.5	349.9	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C8-532AXSP06	236.60	383.9	289.4	328.3	-	241.1	384.9	291.1	329.2	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C8-625AXSP06	273.90	436.2	331.9	374.4	730.9	279.2	437	333.9	375.1	724.5	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB550C8-632AXSP08	273.50	428.3	327.5	368.4	-	275.8	427.4	327.5	367.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550C9-425AXSP06	224.90	365.9	274.9	312.2	-	229.1	366.1	277	313	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C9-432AXSP06	207.00	338.7	253.7	288.8	-	210.8	339.3	255.6	289.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550C9-525AXSP06	253.90	407.9	308.6	349.3	-	258.4	408.6	310.5	349.9	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C9-532AXSP06	236.60	383.9	289.4	328.3	-	241.1	384.9	291.1	329.2	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550C9-625AXSP06	273.90	436.2	331.9	374.4	730.9	279.2	437	333.9	375.1	724.5	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB550C9-632AXSP08	273.50	428.3	327.5	368.4	-	275.8	427.4	327.5	367.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550K2-425AXSP06	215.00	349.5	262.7	298.1	-	219.3	349.7	264.7	299.4	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550K2-432AXSP06	198.50	324.5	243.3	276.9	-	202.3	325.1	245	277.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550K2-525AXSP06	241.60	387.7	293.9	332.3	-	246.2	388.2	295.6	333.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550K2-532AXSP06	225.80	366.3	276.3	313.1	-	230.4	367.3	278.4	314	620	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB550K2-625AXSP08	274.40	425.1	326.3	366.3	-	276.2	423.3	326.4	365.1	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550K2-632AXSP08	260.60	407.6	311.8	350.6	-	262.7	406	311.6	349.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD1554PB550K3-425AXSP06	215.00	349.5	262.7	298.1	-	219.3	349.7	264.7	299.4	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550K3-432AXSP06	198.50	324.5	243.3	276.9	-	202.3	325.1	245	277.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB550K3-525AXSP06	241.60	387.7	293.9	332.3	-	246.2	388.2	295											

EAW-VD1554PB750C2-525AXSP06	268.10	430.9	325.8	369	-	273.2	432	328	370.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C2-532AXSP06	250.40	406.7	305.7	347.3	-	255.5	407.2	308.2	348.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C2-625AXSP06	288.80	459.8	349.3	394.2	-	294.8	461.2	352.2	396	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C2-632AXSP06	273.20	440.1	333.2	376.9	746	279	441.5	335.8	378.8	740.6	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C3-425AXSP06	237.80	387.6	290.7	330.1	-	242.3	388.6	293.1	331.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C3-432AXSP06	219.00	359	268.7	306	-	223.2	359.9	270.8	307.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C3-525AXSP06	268.10	430.9	325.8	369	-	273.2	432	328	370.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C3-532AXSP06	250.40	406.7	305.7	347.3	-	255.5	407.2	308.2	348.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C3-625AXSP06	288.80	459.8	349.3	394.2	-	294.8	461.2	352.2	396	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C3-632AXSP06	273.20	440.1	333.2	376.9	746	279	441.5	335.8	378.8	740.6	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C4-425AXSP06	237.80	387.6	290.7	330.1	-	242.3	388.6	293.1	331.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C4-432AXSP06	219.00	359	268.7	306	-	223.2	359.9	270.8	307.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C4-525AXSP06	268.10	430.9	325.8	369	-	273.2	432	328	370.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C4-532AXSP06	250.40	406.7	305.7	347.3	-	255.5	407.2	308.2	348.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C4-625AXSP06	288.80	459.8	349.3	394.2	-	294.8	461.2	352.2	396	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C4-632AXSP06	273.20	440.1	333.2	376.9	746	279	441.5	335.8	378.8	740.6	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C5-425AXSP06	237.80	387.6	290.7	330.1	-	242.3	388.6	293.1	331.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C5-432AXSP06	219.00	359	268.7	306	-	223.2	359.9	270.8	307.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C5-525AXSP06	268.10	430.9	325.8	369	-	273.2	432	328	370.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C5-532AXSP06	250.40	406.7	305.7	347.3	-	255.5	407.2	308.2	348.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C5-625AXSP06	288.80	459.8	349.3	394.2	-	294.8	461.2	352.2	396	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C5-632AXSP06	273.20	440.1	333.2	376.9	746	279	441.5	335.8	378.8	740.6	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C8-425AXSP06	237.80	387.6	290.7	330.1	-	242.3	388.6	293.1	331.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C8-432AXSP06	219.00	359	268.7	306	-	223.2	359.9	270.8	307.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C8-425AXSP06	268.10	430.9	325.8	369	-	273.2	432	328	370.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C8-532AXSP06	250.40	406.7	305.7	347.3	-	255.5	407.2	308.2	348.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C8-625AXSP06	288.80	459.8	349.3	394.2	-	294.8	461.2	352.2	396	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C8-632AXSP06	273.20	440.1	333.2	376.9	746	279	441.5	335.8	378.8	740.6	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C9-425AXSP06	237.80	387.6	290.7	330.1	-	242.3	388.6	293.1	331.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C9-432AXSP06	219.00	359	268.7	306	-	223.2	359.9	270.8	307.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750C9-525AXSP06	268.10	430.9	325.8	369	-	273.2	432	328	370.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C9-532AXSP06	250.40	406.7	305.7	347.3	-	255.5	407.2	308.2	348.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750C9-625AXSP06	288.80	459.8	349.3	394.2	-	294.8	461.2	352.2	396	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750C9-632AXSP06	273.20	440.1	333.2	376.9	746	279	441.5	335.8	378.8	740.6	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K2-425AXSP06	230.20	374.1	281.3	319.6	-	234.4	375.7	283.3	320.9	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K2-432AXSP06	212.50	347.7	260.4	296.3	-	216.5	349.2	262.7	297.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K2-525AXSP06	259.10	416.2	314.6	356.1	-	263.7	417.5	317	357.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K2-532AXSP06	242.40	392.4	296	335.4	-	247	393.5	298.3	337	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K2-625AXSP06	279.00	444	337.7	380.9	744.3	284.5	445.1	340.3	382.4	739.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K2-632AXSP06	263.80	425.4	322	364.6	719.1	269.5	426.4	324.7	365.5	714.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K3-425AXSP06	230.20	374.1	281.3	319.6	-	234.4	375.7	283.3	320.9	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K3-432AXSP06	212.50	347.7	260.4	296.3	-	216.5	349.2	262.7	297.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K3-525AXSP06	259.10	416.2	314.6	356.1	-	263.7	417.5	317	357.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K3-532AXSP06	242.40	392.4	296	335.4	-	247	393.5	298.3	337	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K3-625AXSP06	279.00	444	337.7	380.9	744.3	284.5	445.1	340.3	382.4	739.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K3-632AXSP06	263.80	425.4	322	364.6	719.1	269.5	426.4	324.7	365.5	714.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K4-425AXSP06	230.20	374.1	281.3	319.6	-	234.4	375.7	283.3	320.9	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K4-432AXSP06	212.50	347.7	260.4	296.3	-	216.5	349.2	262.7	297.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K4-525AXSP06	259.10	416.2	314.6	356.1	-	263.7	417.5	317	357.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K4-532AXSP06	242.40	392.4	296	335.4	-	247	393.5	298.3	337	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K4-625AXSP06	279.00	444	337.7	380.9	744.3	284.5	445.1	340.3	382.4	739.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K4-632AXSP06	263.80	425.4	322	364.6	719.1	269.5	426.4	324.7	365.5	714.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K5-425AXSP06	230.20	374.1	281.3	319.6	-	234.4	375.7	283.3	320.9	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K5-432AXSP06	212.50	347.7	260.4	296.3	-	216.5	349.2	262.7	297.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K5-525AXSP06	259.10	416.2	314.6	356.1	-	263.7	417.5	317	357.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K5-532AXSP06	242.40	392.4	296	335.4	-	247	393.5	298.3	337	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K5-625AXSP06	279.00	444	337.7	380.9	744.3	284.5	445.1	340.3	382.4	739.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K5-632AXSP06	263.80	425.4	322	364.6	719.1	269.5	426.4	324.7	365.5	714.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K8-425AXSP06	230.20	374.1	281.3	319.6	-	234.4	375.7	283.3	320.9	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K8-432AXSP06	212.50	347.7	260.4	296.3	-	216.5	349.2	262.7	297.8	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K8-525AXSP06	259.10	416.2	314.6	356.1	-	263.7	417.5	317	357.3	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K8-532AXSP06	242.40	392.4	296	335.4	-	247	393.5	298.3	337	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD1554PB750K8-625AXSP06	279.00	444	337.7	380.9	744.3	284.5	445.1	340.3	382.4	739.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K8-632AXSP06	263.80	425.4	322	364.6	719.1	269.5	426.4	324.7	365.5	714.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD1554PB750K9-425AXSP06	230.20	374.1	281.3	319.6	-	234.4	375.7	283.3	320.9	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD1554PB750K9-432AXSP06	212.50	347.7	260.4	296.3															

Note: "-" indicates flow rate is outside of unit capability



EAW-VD15S4PI370K2-432AXSP06	216.40	343.7	261	294.5	-	217.9	342.2	260.5	293.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI370K2-525AXSP06	262.80	408.9	313.6	351.9	-	264.2	406	312.4	349.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI370K2-532AXSP06	246.60	387	295.3	332.3	-	248	384.5	294.9	330.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI370K2-625AXSP06	283.50	435.9	336.3	376.1	712.8	284.8	432.4	335.1	373.4	702.3	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI370K2-632AXSP06	268.60	418.1	321.3	360.2	690.6	270.3	415.4	320.4	357.8	681	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI370K4-425AXSP06	234.10	369	281	316.4	-	235.4	366.4	280.5	315.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI370K4-432AXSP06	216.40	343.7	261	294.5	-	217.9	342.2	260.5	293.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI370K4-525AXSP06	262.80	408.9	313.6	351.9	-	264.2	406	312.4	349.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI370K4-532AXSP06	246.60	387	295.3	332.3	-	248	384.5	294.9	330.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI370K4-625AXSP06	283.50	435.9	336.3	376.1	712.8	284.8	432.4	335.1	373.4	702.3	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI370K4-632AXSP06	268.60	418.1	321.3	360.2	690.6	270.3	415.4	320.4	357.8	681	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI370K5-425AXSP06	234.10	369	281	316.4	-	235.4	366.4	280.5	315.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI370K5-432AXSP06	216.40	343.7	261	294.5	-	217.9	342.2	260.5	293.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI370K5-525AXSP06	262.80	408.9	313.6	351.9	-	264.2	406	312.4	349.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI370K5-532AXSP06	246.60	387	295.3	332.3	-	248	384.5	294.9	330.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI370K5-625AXSP06	283.50	435.9	336.3	376.1	712.8	284.8	432.4	335.1	373.4	702.3	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI370K5-632AXSP06	268.60	418.1	321.3	360.2	690.6	270.3	415.4	320.4	357.8	681	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400B3-425AXSP06	237.20	373.6	284.8	320.7	-	238.2	371.6	283.9	319.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400B3-432AXSP06	219.30	348.5	264.5	298.5	-	220.8	346.5	264.1	297.2	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400B3-525AXSP06	266.20	414.5	317.8	356.5	-	267.7	411.7	316.7	354.5	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400B3-532AXSP06	249.80	392.4	299.3	336.9	-	251.4	389.9	298.5	335.2	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400B3-625AXSP06	286.90	440.6	340.3	380.5	721.5	288	437.5	338.8	378.2	710.7	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400B3-632AXSP06	272.50	423.8	325.6	365	700.1	273.9	421.2	324.7	362.7	690.7	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400C3-425AXSP06	242.90	383.2	291.8	328.7	-	243.9	381	291.3	327.3	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400C3-432AXSP06	224.10	356.1	270.5	305.3	-	225.2	354.6	270	303.9	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400C3-525AXSP06	273.50	425.8	326.6	366.6	-	274.7	422.8	325.4	364.5	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400C3-532AXSP06	256.10	402.7	306.9	345.6	-	257.6	400	306.5	343.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400C3-625AXSP06	296.00	455.2	350.8	392.9	745.7	297.1	451.6	349.6	390.2	734.8	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400C3-632AXSP06	280.00	435.9	334.6	375.2	720.5	281.8	432.6	333.6	372.8	710.6	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400C9-425AXSP06	242.90	383.2	291.8	328.7	-	243.9	381	291.3	327.3	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400C9-432AXSP06	224.10	356.1	270.5	305.3	-	225.2	354.6	270	303.9	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400C9-525AXSP06	273.50	425.8	326.6	366.6	-	274.7	422.8	325.4	364.5	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400C9-532AXSP06	256.10	402.7	306.9	345.6	-	257.6	400	306.5	343.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400C9-625AXSP06	296.00	455.2	350.8	392.9	745.7	297.1	451.6	349.6	390.2	734.8	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400C9-632AXSP06	280.00	435.9	334.6	375.2	720.5	281.8	432.6	333.6	372.8	710.6	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400K3-425AXSP06	234.10	369	281	316.4	-	235.4	366.4	280.5	315.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400K3-432AXSP06	216.40	343.7	261	294.5	-	217.9	342.2	260.5	293.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400K3-525AXSP06	262.80	408.9	313.6	351.9	-	264.2	406	312.4	349.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400K3-532AXSP06	246.60	387	295.3	332.3	-	248	384.5	294.9	330.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400K3-625AXSP06	283.50	435.9	336.3	376.1	712.8	284.8	432.4	335.1	373.4	702.3	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400K3-632AXSP06	268.60	418.1	321.3	360.2	690.6	270.3	415.4	320.4	357.8	681	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400K9-425AXSP06	234.10	369	281	316.4	-	235.4	366.4	280.5	315.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400K9-432AXSP06	216.40	343.7	261	294.5	-	217.9	342.2	260.5	293.1	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400K9-525AXSP06	262.80	408.9	313.6	351.9	-	264.2	406	312.4	349.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400K9-532AXSP06	246.60	387	295.3	332.3	-	248	384.5	294.9	330.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400K9-625AXSP06	283.50	435.9	336.3	376.1	712.8	284.8	432.4	335.1	373.4	702.3	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400K9-632AXSP06	268.60	418.1	321.3	360.2	690.6	270.3	415.4	320.4	357.8	681	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400R3-425AXSP06	238.60	376.5	286.5	323.2	-	240.1	374	286.2	321.5	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400R3-432AXSP06	220.60	350.8	266.1	300.9	-	222.2	348.9	265.8	299.2	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI400R3-525AXSP06	268.10	417	319.6	359.2	-	269.3	414.2	319	356.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400R3-532AXSP06	251.70	394.9	301.6	339.5	-	252.9	392.4	300.9	337.3	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI400R3-625AXSP06	289.10	444.8	343	383.6	727.5	290.6	441.4	341.8	381.1	717.1	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI400R3-632AXSP06	274.10	426.9	327.5	367.7	705.4	275.9	423.8	326.6	365.4	695.1	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550B3-425AXSP04	241.40	400.2	300.2	341.5	685.3	247.7	400.7	302.6	342.6	679.2	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550B3-432AXSP06	240.00	382.4	290	327.8	-	241.6	380.7	289.4	326.2	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550B3-525AXSP06	292.90	457.5	350.2	393.3	-	294.7	458.8	349.4	391.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550B3-532AXSP06	274.50	432	329.4	371.3	-	276.3	430	329.1	369.4	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550B3-625AXSP06	316.50	487.8	375.8	420.7	-	318.3	485	374.8	418.7	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550B3-632AXSP06	300.70	468	358.5	403	-	302.3	465.2	358.1	401	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550C2-425AXSP04	253.10	418.2	314.1	357	718.7	259.3	419.3	316.6	358.1	712	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550C2-432AXSP04	231.40	387.9	289.4	330.2	670	237.7	388.4	292.2	331.4	664.3	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550C2-525AXSP04	282.00	464.2	349.4	397.2	787.2	289.8	464.4	352.2	398	779.3	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI550C2-532AXSP06	287.20	453.1	344.9	388.4	-	288.9	449.9	344.3	386.8	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550C2-625AXSP06	334.70	516.9	397.7	445.3	-	335.9	513.2	396.1	442.7	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550C2-632AXSP06	315.90	492.8	377.5	423.9	-	317.5	489.6	376.3	421.7	-	451	29.2							

EAW-VD15S4PI550K2-425AXSP04	242.20	400.8	301.1	342	687.5	248.5	401.4	303.1	343.1	680.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550K2-432AXSP06	240.60	383.7	290.4	328.4	-	242.4	382	290.5	327.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550K2-525AXSP06	293.90	459.1	351.4	394.7	-	295.6	456.4	350.5	392.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K2-532AXSP06	275.00	433.6	330	372	-	276.7	430.7	329.6	370	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K2-625AXSP06	318.40	490.9	378.1	423.3	-	320	487.6	376.8	420.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K2-632AXSP06	301.70	469.7	360.3	404.4	-	303.2	466.7	359.2	402.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K3-425AXSP04	242.20	400.8	301.1	342	687.5	248.5	401.4	303.1	343.1	680.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550K3-432AXSP06	240.60	383.7	290.4	328.4	-	242.4	382	290.5	327.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550K3-525AXSP06	293.90	459.1	351.4	394.7	-	295.6	456.4	350.5	392.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K3-532AXSP06	275.00	433.6	330	372	-	276.7	430.7	329.6	370	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K3-625AXSP06	318.40	490.9	378.1	423.3	-	320	487.6	376.8	420.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K3-632AXSP06	301.70	469.7	360.3	404.4	-	303.2	466.7	359.2	402.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K4-425AXSP04	242.20	400.8	301.1	342	687.5	248.5	401.4	303.1	343.1	680.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550K4-432AXSP06	240.60	383.7	290.4	328.4	-	242.4	382	290.5	327.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550K4-525AXSP06	293.90	459.1	351.4	394.7	-	295.6	456.4	350.5	392.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K4-532AXSP06	275.00	433.6	330	372	-	276.7	430.7	329.6	370	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K4-625AXSP06	318.40	490.9	378.1	423.3	-	320	487.6	376.8	420.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K4-632AXSP06	301.70	469.7	360.3	404.4	-	303.2	466.7	359.2	402.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K5-425AXSP04	242.20	400.8	301.1	342	687.5	248.5	401.4	303.1	343.1	680.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550K5-432AXSP06	240.60	383.7	290.4	328.4	-	242.4	382	290.5	327.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550K5-525AXSP06	293.90	459.1	351.4	394.7	-	295.6	456.4	350.5	392.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K5-532AXSP06	275.00	433.6	330	372	-	276.7	430.7	329.6	370	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K5-625AXSP06	318.40	490.9	378.1	423.3	-	320	487.6	376.8	420.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K5-632AXSP06	301.70	469.7	360.3	404.4	-	303.2	466.7	359.2	402.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K8-425AXSP04	242.20	400.8	301.1	342	687.5	248.5	401.4	303.1	343.1	680.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550K8-432AXSP06	240.60	383.7	290.4	328.4	-	242.4	382	290.5	327.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550K8-525AXSP06	293.90	459.1	351.4	394.7	-	295.6	456.4	350.5	392.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K8-532AXSP06	275.00	433.6	330	372	-	276.7	430.7	329.6	370	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K8-625AXSP06	318.40	490.9	378.1	423.3	-	320	487.6	376.8	420.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K8-632AXSP06	301.70	469.7	360.3	404.4	-	303.2	466.7	359.2	402.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K9-425AXSP04	242.20	400.8	301.1	342	687.5	248.5	401.4	303.1	343.1	680.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550K9-432AXSP06	240.60	383.7	290.4	328.4	-	242.4	382	290.5	327.4	-	293	27.1	3"	234	22.2	2"	352	38	3"
EAW-VD15S4PI550K9-525AXSP06	293.90	459.1	351.4	394.7	-	295.6	456.4	350.5	392.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K9-532AXSP06	275.00	433.6	330	372	-	276.7	430.7	329.6	370	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550K9-625AXSP06	318.40	490.9	378.1	423.3	-	320	487.6	376.8	420.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550K9-632AXSP06	301.70	469.7	360.3	404.4	-	303.2	466.7	359.2	402.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550R3-425AXSP04	249.00	411.6	308.8	351.6	706.9	255.3	412.4	311.6	352.9	699.9	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550R3-432AXSP04	228.20	382.9	285.6	326.1	660.9	234.8	383.7	288.3	327.5	655.9	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI550R3-525AXSP06	302.10	471.7	361.2	405.9	-	303.5	469.1	360.5	403.6	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550R3-532AXSP06	282.60	445.4	339.2	381.9	-	284.5	442.6	339	380.7	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD15S4PI550R3-625AXSP06	327.00	504.6	388.4	434.9	-	329	501.7	387.4	432.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI550R3-632AXSP06	310.00	483.2	369.8	415.8	-	311.7	480.3	369.4	413.2	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C2-425AXSP04	271.80	448.7	336.4	382.3	-	278.5	450	339.3	384.3	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C2-432AXSP04	248.60	415.6	310.4	353.9	719.6	255.5	416.9	313.2	355.6	714.5	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C2-525AXSP04	303.00	496.9	374.7	425.2	846	311.1	498	378	426.9	837.8	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C2-532AXSP04	280.70	467.1	349.7	398.7	801	288.8	468.8	353.5	400.2	794.4	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C2-625AXSP06	357.40	553.4	425	476.9	-	359.4	550.5	424.1	474.4	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C2-632AXSP06	337.60	528.4	403.8	453.9	-	340	525.1	403.3	452.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C3-425AXSP04	271.80	448.7	336.4	382.3	-	278.5	450	339.3	384.3	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C3-432AXSP04	248.60	415.6	310.4	353.9	719.6	255.5	416.9	313.2	355.6	714.5	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C3-525AXSP04	303.00	496.9	374.7	425.2	846	311.1	498	378	426.9	837.8	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C3-532AXSP04	280.70	467.1	349.7	398.7	801	288.8	468.8	353.5	400.2	794.4	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C3-625AXSP06	357.40	553.4	425	476.9	-	359.4	550.5	424.1	474.4	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C3-632AXSP06	337.60	528.4	403.8	453.9	-	340	525.1	403.3	452.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C4-425AXSP04	271.80	448.7	336.4	382.3	-	278.5	450	339.3	384.3	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C4-432AXSP04	248.60	415.6	310.4	353.9	719.6	255.5	416.9	313.2	355.6	714.5	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C4-525AXSP04	303.00	496.9	374.7	425.2	846	311.1	498	378	426.9	837.8	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C4-532AXSP04	280.70	467.1	349.7	398.7	801	288.8	468.8	353.5	400.2	794.4	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C4-625AXSP06	357.40	553.4	425	476.9	-	359.4	550.5	424.1	474.4	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C4-632AXSP06	337.60	528.4	403.8	453.9	-	340	525.1	403.3	452.3	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD15S4PI750C8-425AXSP04	271.80	448.7	336.4	382.3	-	278.5	450	339.3	384.3	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C8-432AXSP04	248.60	415.6	310.4	353.9	719.6	255.5	416.9	313.2	355.6	714.5	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD15S4PI750C8-525AXSP04	303.00	496.9	374.7	425.2	846	311.1	498	378	426.9	837.8	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C8-532AXSP04	280.70	467.1	349.7	398.7	801	288.8	468.8	353.5	400.2	794.4	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD15S4PI750C8-625AXSP06	357.40	553.4	425																

EAW-VD1554P1750K5-632AXSP06	326.40	509.3	389.7	437.8	-	328	506.6	389	436.1	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554P1750K8-425AXSP04	262.50	433.5	324.9	369.7	745.2	269.6	434.7	328.2	371.5	739.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD1554P1750K8-432AXSP04	240.60	402.6	301	343	697	247.4	403.9	303.7	344.1	691.1	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD1554P1750K8-525AXSP04	291.80	479.7	361.1	410.2	814.6	299.8	480.6	364.7	411.6	807.4	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD1554P1750K8-532AXSP06	296.80	469.3	357.2	402.5	-	299.2	466.8	356.7	400.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD1554P1750K8-625AXSP06	344.10	532	409.5	458.8	-	346.1	529.4	408.8	457	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554P1750K8-632AXSP06	326.40	509.3	389.7	437.8	-	328	506.6	389	436.1	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554P1750K9-425AXSP04	262.50	433.5	324.9	369.7	745.2	269.6	434.7	328.2	371.5	739.4	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD1554P1750K9-432AXSP04	240.60	402.6	301	343	697	247.4	403.9	303.7	344.1	691.1	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD1554P1750K9-525AXSP04	291.80	479.7	361.1	410.2	814.6	299.8	480.6	364.7	411.6	807.4	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD1554P1750K9-532AXSP06	296.80	469.3	357.2	402.5	-	299.2	466.8	356.7	400.9	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD1554P1750K9-625AXSP06	344.10	532	409.5	458.8	-	346.1	529.4	408.8	457	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554P1750K9-632AXSP06	326.40	509.3	389.7	437.8	-	328	506.6	389	436.1	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554P1750R3-425AXSP04	257.00	424.7	318.2	361.8	729.3	263.6	425.9	321.3	363.6	723.6	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD1554P1750R3-432AXSP04	235.60	394.4	294.6	336.2	682	242.2	395.6	297.5	337.3	677.3	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD1554P1750R3-525AXSP04	284.90	468.6	353	400.8	796	293.2	470	356.4	402.2	788	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD1554P1750R3-532AXSP06	291.10	458.9	349.6	393.8	-	292.8	457	349	392.2	-	372	28	3"	298	18.5	3"	446	39.4	3"
EAW-VD1554P1750R3-625AXSP06	336.40	519.5	399.6	447.6	-	338.2	516.9	398.9	445.8	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554P1750R3-632AXSP06	319.10	498.1	380.8	428.4	-	321.1	495.4	380.7	426	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD1554PK370C2-425AXSP06	217.20	348.2	263.2	297.7	-	219.8	347.8	264	297.9	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C2-432AXSP06	200.50	323.7	243.8	276.5	-	203.2	323.3	244.6	276.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C2-525AXSP06	244.50	386.9	294.5	331.7	-	247.3	385.8	295.3	331.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C2-532AXSP06	228.40	365.5	276.9	313.1	617.6	231.5	364.6	277.9	312.8	611.3	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C2-625AXSP06	262.50	412.8	316.1	355.1	683.1	266	411.2	316.4	354.2	675.5	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK370C2-632AXSP08	261.90	405.2	311.3	348.9	-	262.7	402.6	310.3	347	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370C4-425AXSP06	217.20	348.2	263.2	297.7	-	219.8	347.8	264	297.9	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C4-432AXSP06	200.50	323.7	243.8	276.5	-	203.2	323.3	244.6	276.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C4-525AXSP06	244.50	386.9	294.5	331.7	-	247.3	385.8	295.3	331.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C4-532AXSP06	228.40	365.5	276.9	313.1	617.6	231.5	364.6	277.9	312.8	611.3	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C4-625AXSP06	262.50	412.8	316.1	355.1	683.1	266	411.2	316.4	354.2	675.5	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK370C4-632AXSP08	261.90	405.2	311.3	348.9	-	262.7	402.6	310.3	347	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370C5-425AXSP06	217.20	348.2	263.2	297.7	-	219.8	347.8	264	297.9	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C5-432AXSP06	200.50	323.7	243.8	276.5	-	203.2	323.3	244.6	276.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C5-525AXSP06	244.50	386.9	294.5	331.7	-	247.3	385.8	295.3	331.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C5-532AXSP06	228.40	365.5	276.9	313.1	617.6	231.5	364.6	277.9	312.8	611.3	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C5-625AXSP06	262.50	412.8	316.1	355.1	683.1	266	411.2	316.4	354.2	675.5	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK370C5-632AXSP08	261.90	405.2	311.3	348.9	-	262.7	402.6	310.3	347	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370C8-425AXSP06	217.20	348.2	263.2	297.7	-	219.8	347.8	264	297.9	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C8-432AXSP06	200.50	323.7	243.8	276.5	-	203.2	323.3	244.6	276.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370C8-525AXSP06	244.50	386.9	294.5	331.7	-	247.3	385.8	295.3	331.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C8-532AXSP06	228.40	365.5	276.9	313.1	617.6	231.5	364.6	277.9	312.8	611.3	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370C8-625AXSP06	262.50	412.8	316.1	355.1	683.1	266	411.2	316.4	354.2	675.5	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK370C8-632AXSP08	261.90	405.2	311.3	348.9	-	262.7	402.6	310.3	347	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K2-425AXSP06	209.30	334.8	253.4	287	-	211.7	334.2	254.1	286.5	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K2-432AXSP06	193.40	311.9	235.3	266.7	-	196	311.9	236	266.7	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K2-525AXSP06	234.70	371.3	283	319.1	-	237.6	370.6	283.6	318.5	614.4	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370K2-532AXSP06	219.60	351.7	266.5	301.6	593.5	222.5	350.8	267.4	300.8	586.6	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370K2-625AXSP08	264.30	404.4	312.4	349.4	-	265	401.6	311.5	346.9	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K2-632AXSP08	251.80	389.4	299.1	335.5	-	252.8	386.7	298	333.1	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K4-425AXSP06	209.30	334.8	253.4	287	-	211.7	334.2	254.1	286.5	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K4-432AXSP06	193.40	311.9	235.3	266.7	-	196	311.9	236	266.7	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K4-525AXSP06	234.70	371.3	283	319.1	-	237.6	370.6	283.6	318.5	614.4	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370K4-532AXSP06	219.60	351.7	266.5	301.6	593.5	222.5	350.8	267.4	300.8	586.6	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370K4-625AXSP08	264.30	404.4	312.4	349.4	-	265	401.6	311.5	346.9	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K4-632AXSP08	251.80	389.4	299.1	335.5	-	252.8	386.7	298	333.1	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K5-425AXSP06	209.30	334.8	253.4	287	-	211.7	334.2	254.1	286.5	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K5-432AXSP06	193.40	311.9	235.3	266.7	-	196	311.9	236	266.7	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K5-525AXSP06	234.70	371.3	283	319.1	-	237.6	370.6	283.6	318.5	614.4	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370K5-532AXSP06	219.60	351.7	266.5	301.6	593.5	222.5	350.8	267.4	300.8	586.6	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK370K5-625AXSP08	264.30	404.4	312.4	349.4	-	265	401.6	311.5	346.9	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K5-632AXSP08	251.80	389.4	299.1	335.5	-	252.8	386.7	298	333.1	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK370K8-425AXSP06	209.30	334.8	253.4	287	-	211.7	334.2	254.1	286.5	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K8-432AXSP06	193.40	311.9	235.3	266.7	-	196	311.9	236	266.7	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK370K8-525AXSP06	234.70	371.3	283	319.1	-	237.6	370.6	283.6	318.5	614.4	372	24.1	3"	298	15				

EAW-VD1554PK400R3-625AXSP08	268.60	411.8	318	355.3	-	269.5	409.1	316.8	353.3	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK400R3-632AXSP08	256.10	396.3	304.3	341.4	-	256.9	393.8	303.3	339.1	-	338	30.8	3"	270	20.4	3"	406	43.2	3"
EAW-VD1554PK500R3-425AXSP06	231.10	371.6	280.5	317.7	-	234	371.2	281.4	317.9	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK500R3-432AXSP06	213.40	345.6	259.9	295.1	-	216.2	345.1	261.1	295.2	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK500R3-525AXSP06	259.80	411.9	312.8	353.2	-	262.9	411.4	314.2	353.3	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK500R3-532AXSP06	243.20	389.4	294.8	333.6	-	246.8	389.4	296	333.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK500R3-625AXSP06	278.90	437.9	335.2	376.8	727.4	282.9	437.8	336.3	376.7	720	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK500R3-632AXSP06	264.90	421.1	320.6	361.6	705.4	269.1	420.9	321.8	361.5	698.4	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C2-425AXSP06	242.20	389.9	294.1	333.5	-	245.5	389.3	295.1	333.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C2-432AXSP06	222.80	361.2	271.5	308.1	-	225.8	360.5	272.7	308.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C2-525AXSP06	274.20	435.4	330.5	373.5	-	277.4	434.7	331.8	373.4	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C2-532AXSP06	255.80	409.5	309.8	350.9	-	258.9	409	310.8	350.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C2-625AXSP06	297.30	466.5	356.4	401	-	300.8	465.9	357.8	401	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C2-632AXSP06	280.50	445.7	338.7	382.3	747.9	284.4	444.7	339.8	382	739.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C3-425AXSP06	242.20	389.9	294.1	333.5	-	245.5	389.3	295.1	333.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C3-432AXSP06	222.80	361.2	271.5	308.1	-	225.8	360.5	272.7	308.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C3-525AXSP06	274.20	435.4	330.5	373.5	-	277.4	434.7	331.8	373.4	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C3-532AXSP06	255.80	409.5	309.8	350.9	-	258.9	409	310.8	350.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C3-625AXSP06	297.30	466.5	356.4	401	-	300.8	465.9	357.8	401	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C3-632AXSP06	280.50	445.7	338.7	382.3	747.9	284.4	444.7	339.8	382	739.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C4-425AXSP06	242.20	389.9	294.1	333.5	-	245.5	389.3	295.1	333.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C4-432AXSP06	222.80	361.2	271.5	308.1	-	225.8	360.5	272.7	308.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C4-525AXSP06	274.20	435.4	330.5	373.5	-	277.4	434.7	331.8	373.4	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C4-532AXSP06	255.80	409.5	309.8	350.9	-	258.9	409	310.8	350.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C4-625AXSP06	297.30	466.5	356.4	401	-	300.8	465.9	357.8	401	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C4-632AXSP06	280.50	445.7	338.7	382.3	747.9	284.4	444.7	339.8	382	739.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C5-425AXSP06	242.20	389.9	294.1	333.5	-	245.5	389.3	295.1	333.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C5-432AXSP06	222.80	361.2	271.5	308.1	-	225.8	360.5	272.7	308.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C5-525AXSP06	274.20	435.4	330.5	373.5	-	277.4	434.7	331.8	373.4	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C5-532AXSP06	255.80	409.5	309.8	350.9	-	258.9	409	310.8	350.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C5-625AXSP06	297.30	466.5	356.4	401	-	300.8	465.9	357.8	401	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C5-632AXSP06	280.50	445.7	338.7	382.3	747.9	284.4	444.7	339.8	382	739.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C8-425AXSP06	242.20	389.9	294.1	333.5	-	245.5	389.3	295.1	333.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C8-432AXSP06	222.80	361.2	271.5	308.1	-	225.8	360.5	272.7	308.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C8-525AXSP06	274.20	435.4	330.5	373.5	-	277.4	434.7	331.8	373.4	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C8-532AXSP06	255.80	409.5	309.8	350.9	-	258.9	409	310.8	350.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C8-625AXSP06	297.30	466.5	356.4	401	-	300.8	465.9	357.8	401	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C8-632AXSP06	280.50	445.7	338.7	382.3	747.9	284.4	444.7	339.8	382	739.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C9-425AXSP06	242.20	389.9	294.1	333.5	-	245.5	389.3	295.1	333.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C9-432AXSP06	222.80	361.2	271.5	308.1	-	225.8	360.5	272.7	308.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550C9-525AXSP06	274.20	435.4	330.5	373.5	-	277.4	434.7	331.8	373.4	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C9-532AXSP06	255.80	409.5	309.8	350.9	-	258.9	409	310.8	350.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550C9-625AXSP06	297.30	466.5	356.4	401	-	300.8	465.9	357.8	401	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550C9-632AXSP06	280.50	445.7	338.7	382.3	747.9	284.4	444.7	339.8	382	739.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K2-425AXSP06	232.00	372.5	281.6	319	-	235.2	372.5	282.4	319	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K2-432AXSP06	214.10	346.4	260.8	295.8	-	216.9	345.8	261.6	295.8	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K2-525AXSP06	261.20	414.3	315.1	355.7	-	264.7	413.7	316.3	355.2	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550K2-532AXSP06	244.40	391.4	296.2	335.3	-	248.2	391	297.2	334.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550K2-625AXSP06	281.70	442.4	338.5	380.6	735	285.4	441.7	339.2	380	726.6	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K2-632AXSP06	266.80	424.2	322.9	364.2	710.6	270.5	423.3	324	364	703.3	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K3-425AXSP06	232.00	372.5	281.6	319	-	235.2	372.5	282.4	319	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K3-432AXSP06	214.10	346.4	260.8	295.8	-	216.9	345.8	261.6	295.8	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K3-525AXSP06	261.20	414.3	315.1	355.7	-	264.7	413.7	316.3	355.2	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550K3-532AXSP06	244.40	391.4	296.2	335.3	-	248.2	391	297.2	334.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550K3-625AXSP06	281.70	442.4	338.5	380.6	735	285.4	441.7	339.2	380	726.6	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K3-632AXSP06	266.80	424.2	322.9	364.2	710.6	270.5	423.3	324	364	703.3	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K4-425AXSP06	232.00	372.5	281.6	319	-	235.2	372.5	282.4	319	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K4-432AXSP06	214.10	346.4	260.8	295.8	-	216.9	345.8	261.6	295.8	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K4-525AXSP06	261.20	414.3	315.1	355.7	-	264.7	413.7	316.3	355.2	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550K4-532AXSP06	244.40	391.4	296.2	335.3	-	248.2	391	297.2	334.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK550K4-625AXSP06	281.70	442.4	338.5	380.6	735	285.4	441.7	339.2	380	726.6	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K4-632AXSP06	266.80	424.2	322.9	364.2	710.6	270.5	423.3	324	364	703.3	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK550K5-425AXSP06	232.00	372.5	281.6	319	-	235.2	372.5	282.4	319	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K5-432AXSP06	214.10	346.4	260.8	295.8	-	216.9	345.8	261.6	295.8	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK550K5-525AXSP06	261.20																		

EAW-VD1554PK750C4-532AXSP06	271.30	436.1	329.6	372.5	-	275.2	435.8	330.9	372.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C4-625AXSP06	314.40	494.8	377.4	424.8	-	318.5	494.5	379.1	425.2	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C4-632AXSP06	297.60	473.1	359.2	405.9	-	302	472.9	361.1	405.7	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C5-425AXSP04	233.00	399.8	296.3	339.1	698.2	242.9	403.3	301.2	342.9	694.8	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750C5-432AXSP06	236.80	384.1	288.8	328	-	240.1	384.8	290.4	328.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750C5-525AXSP06	290.40	462.8	350.9	396.3	-	294.4	462.9	352.5	397	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C5-532AXSP06	271.30	436.1	329.6	372.5	-	275.2	435.8	330.9	372.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C5-625AXSP06	314.40	494.8	377.4	424.8	-	318.5	494.5	379.1	425.2	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C5-632AXSP06	297.60	473.1	359.2	405.9	-	302	472.9	361.1	405.7	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C8-425AXSP04	233.00	399.8	296.3	339.1	698.2	242.9	403.3	301.2	342.9	694.8	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750C8-432AXSP06	236.80	384.1	288.8	328	-	240.1	384.8	290.4	328.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750C8-525AXSP06	290.40	462.8	350.9	396.3	-	294.4	462.9	352.5	397	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C8-532AXSP06	271.30	436.1	329.6	372.5	-	275.2	435.8	330.9	372.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C8-625AXSP06	314.40	494.8	377.4	424.8	-	318.5	494.5	379.1	425.2	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C8-632AXSP06	297.60	473.1	359.2	405.9	-	302	472.9	361.1	405.7	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C9-425AXSP04	233.00	399.8	296.3	339.1	698.2	242.9	403.3	301.2	342.9	694.8	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750C9-432AXSP06	236.80	384.1	288.8	328	-	240.1	384.8	290.4	328.6	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750C9-525AXSP06	290.40	462.8	350.9	396.3	-	294.4	462.9	352.5	397	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C9-532AXSP06	271.30	436.1	329.6	372.5	-	275.2	435.8	330.9	372.9	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750C9-625AXSP06	314.40	494.8	377.4	424.8	-	318.5	494.5	379.1	425.2	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750C9-632AXSP06	297.60	473.1	359.2	405.9	-	302	472.9	361.1	405.7	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K2-425AXSP04	224.80	386.4	286.3	328.1	674.6	234.7	389.7	291.6	331.7	671.3	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750K2-432AXSP06	229.60	372.4	280	317.7	-	232.9	372.3	281.1	318.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750K2-525AXSP06	280.60	446.2	338.9	382.5	-	284.4	446.2	340.3	382.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K2-532AXSP06	262.40	420.8	318.5	360.4	-	266.2	421.3	319.8	360.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K2-625AXSP06	303.30	476.4	364.3	409.9	-	307.3	476.4	365.6	409.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K2-632AXSP06	287.20	456.3	347	391.2	-	291.3	456.1	348.2	391.6	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K3-425AXSP04	224.80	386.4	286.3	328.1	674.6	234.7	389.7	291.6	331.7	671.3	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750K3-432AXSP06	229.60	372.4	280	317.7	-	232.9	372.3	281.1	318.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750K3-525AXSP06	280.60	446.2	338.9	382.5	-	284.4	446.2	340.3	382.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K3-532AXSP06	262.40	420.8	318.5	360.4	-	266.2	421.3	319.8	360.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K3-625AXSP06	303.30	476.4	364.3	409.9	-	307.3	476.4	365.6	409.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K3-632AXSP06	287.20	456.3	347	391.2	-	291.3	456.1	348.2	391.6	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K4-425AXSP04	224.80	386.4	286.3	328.1	674.6	234.7	389.7	291.6	331.7	671.3	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750K4-432AXSP06	229.60	372.4	280	317.7	-	232.9	372.3	281.1	318.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750K4-525AXSP06	280.60	446.2	338.9	382.5	-	284.4	446.2	340.3	382.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K4-532AXSP06	262.40	420.8	318.5	360.4	-	266.2	421.3	319.8	360.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K4-625AXSP06	303.30	476.4	364.3	409.9	-	307.3	476.4	365.6	409.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K4-632AXSP06	287.20	456.3	347	391.2	-	291.3	456.1	348.2	391.6	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K5-425AXSP04	224.80	386.4	286.3	328.1	674.6	234.7	389.7	291.6	331.7	671.3	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750K5-432AXSP06	229.60	372.4	280	317.7	-	232.9	372.3	281.1	318.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750K5-525AXSP06	280.60	446.2	338.9	382.5	-	284.4	446.2	340.3	382.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K5-532AXSP06	262.40	420.8	318.5	360.4	-	266.2	421.3	319.8	360.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K5-625AXSP06	303.30	476.4	364.3	409.9	-	307.3	476.4	365.6	409.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K5-632AXSP06	287.20	456.3	347	391.2	-	291.3	456.1	348.2	391.6	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K8-425AXSP04	224.80	386.4	286.3	328.1	674.6	234.7	389.7	291.6	331.7	671.3	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750K8-432AXSP06	229.60	372.4	280	317.7	-	232.9	372.3	281.1	318.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750K8-525AXSP06	280.60	446.2	338.9	382.5	-	284.4	446.2	340.3	382.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K8-532AXSP06	262.40	420.8	318.5	360.4	-	266.2	421.3	319.8	360.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K8-625AXSP06	303.30	476.4	364.3	409.9	-	307.3	476.4	365.6	409.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K8-632AXSP06	287.20	456.3	347	391.2	-	291.3	456.1	348.2	391.6	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K9-425AXSP04	224.80	386.4	286.3	328.1	674.6	234.7	389.7	291.6	331.7	671.3	451	18.1	3"	361	11.9	3"	541	21.8	4"
EAW-VD1554PK750K9-432AXSP06	229.60	372.4	280	317.7	-	232.9	372.3	281.1	318.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750K9-525AXSP06	280.60	446.2	338.9	382.5	-	284.4	446.2	340.3	382.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K9-532AXSP06	262.40	420.8	318.5	360.4	-	266.2	421.3	319.8	360.8	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750K9-625AXSP06	303.30	476.4	364.3	409.9	-	307.3	476.4	365.6	409.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750K9-632AXSP06	287.20	456.3	347	391.2	-	291.3	456.1	348.2	391.6	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750R3-425AXSP06	244.00	392.6	296.6	335.7	-	247.6	392.8	297.6	335.9	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750R3-432AXSP06	225.00	364.7	274.3	311.4	-	228.4	364.6	275.6	312	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD1554PK750R3-525AXSP06	274.30	436.2	331.1	374.2	-	278.3	436.2	332.4	374.1	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750R3-532AXSP06	257.30	412	311.6	352.4	-	260.9	411.7	313.3	352.7	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD1554PK750R3-625AXSP06	296.10	465.4	355.6	400	-	300.5	464.7	356.8	399.9	-	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554PK750R3-632AXSP06	280.80	446.3	339.1	382.8	748.8	284.7	445.9	340.7	383	741.9	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD1554ZB370C2-425AXSP08	248.70	391.8	298.5	336.5	-	250	389.3	297.8	334.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB370C2-432AXSP08																			

EAW-VD1554ZB370K5-525AXSP08	263.20	409.6	314.1	352.4	-	264.6	406.6	312.9	350.3	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB370K5-532AXSP08	247.20	387.5	296.1	332.7	-	248.3	384.9	295.3	331	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB370K5-625AXSP08	284.10	436.9	337	376.9	714.5	285.4	433.4	335.7	374.2	703.9	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB370K5-632AXSP08	269.50	418.9	321.9	360.8	691.9	270.7	416.1	320.9	358.4	681.4	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB370K8-425AXSP08	239.60	377.3	287.4	323.9	-	240.8	374.4	286.8	321.8	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB370K8-432AXSP08	222.00	352	267.4	301.9	-	223.3	349.7	266.8	300.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB370K8-525AXSP08	263.20	409.6	314.1	352.4	-	264.6	406.6	312.9	350.3	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB370K8-532AXSP08	247.20	387.5	296.1	332.7	-	248.3	384.9	295.3	331	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB370K8-625AXSP08	284.10	436.9	337	376.9	714.5	285.4	433.4	335.7	374.2	703.9	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB370K8-632AXSP08	269.50	418.9	321.9	360.8	691.9	270.7	416.1	320.9	358.4	681.4	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400K3-425AXSP08	242.80	382	291.3	327.8	-	244.2	379.8	290.8	326.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400K3-432AXSP08	225.00	357	271	305.6	-	226.3	354.7	270.5	304.1	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400K3-525AXSP08	266.60	414.7	318.3	357.2	-	268.2	412.3	317.2	355.1	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400K3-532AXSP08	250.10	392.9	299.6	337.3	-	251.7	390.4	298.9	335.6	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400K3-625AXSP08	287.50	441.8	341.1	381.5	723.4	288.7	438.5	339.6	379.1	712.5	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400K3-632AXSP08	273.00	424.6	326.2	365.7	701.6	274.4	422	325.2	363.4	692	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400C3-425AXSP08	248.70	391.8	298.5	336.5	-	250	389.3	297.8	334.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400C3-432AXSP08	229.90	364.7	277.1	312.6	-	231.3	362.9	276.5	311	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400C3-525AXSP08	273.90	426.5	327.1	367.2	-	275.5	423.5	325.9	365	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400C3-532AXSP08	256.70	403.2	307.7	345.9	-	257.8	400.4	306.7	344	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400C3-625AXSP08	296.60	456.2	351.5	393.7	747.4	297.6	452.5	350.2	391	736.3	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400C3-632AXSP08	280.80	436.6	335.1	375.8	721.9	282.2	433.3	334.1	373.9	711.9	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400C9-425AXSP08	248.70	391.8	298.5	336.5	-	250	389.3	297.8	334.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400C9-432AXSP08	229.90	364.7	277.1	312.6	-	231.3	362.9	276.5	311	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400C9-525AXSP08	273.90	426.5	327.1	367.2	-	275.5	423.5	325.9	365	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400C9-532AXSP08	256.70	403.2	307.7	345.9	-	257.8	400.4	306.7	344	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400C9-625AXSP08	296.60	456.2	351.5	393.7	747.4	297.6	452.5	350.2	391	736.3	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400C9-632AXSP08	280.80	436.6	335.1	375.8	721.9	282.2	433.3	334.1	373.9	711.9	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400K3-425AXSP08	239.60	377.3	287.4	323.9	-	240.8	374.4	286.8	321.8	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400K3-432AXSP08	222.00	352	267.4	301.9	-	223.3	349.7	266.8	300.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400K3-525AXSP08	263.20	409.6	314.1	352.4	-	264.6	406.6	312.9	350.3	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400K3-532AXSP08	247.20	387.5	296.1	332.7	-	248.3	384.9	295.3	331	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400K3-625AXSP08	284.10	436.9	337	376.9	714.5	285.4	433.4	335.7	374.2	703.9	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400K3-632AXSP08	269.50	418.9	321.9	360.8	691.9	270.7	416.1	320.9	358.4	681.4	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400K9-425AXSP08	239.60	377.3	287.4	323.9	-	240.8	374.4	286.8	321.8	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400K9-432AXSP08	222.00	352	267.4	301.9	-	223.3	349.7	266.8	300.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400K9-525AXSP08	263.20	409.6	314.1	352.4	-	264.6	406.6	312.9	350.3	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400K9-532AXSP08	247.20	387.5	296.1	332.7	-	248.3	384.9	295.3	331	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400K9-625AXSP08	284.10	436.9	337	376.9	714.5	285.4	433.4	335.7	374.2	703.9	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400K9-632AXSP08	269.50	418.9	321.9	360.8	691.9	270.7	416.1	320.9	358.4	681.4	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400R3-425AXSP08	244.30	385.1	293.1	330.4	-	245.7	382.4	292.6	328.5	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400R3-432AXSP08	226.30	359.4	272.7	308.1	-	227.8	357.2	272.2	306.7	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB400R3-525AXSP08	268.60	417.8	320.2	359.8	-	269.7	414.9	319.5	357.3	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400R3-532AXSP08	252.00	395.4	302	339.9	-	253.2	393	301.2	337.8	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB400R3-625AXSP08	289.70	445.8	343.8	384.5	729.3	291.2	442.4	342.6	381.9	718.8	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB400R3-632AXSP08	275.00	427.8	328.6	368.4	706.9	276.4	424.6	327.2	366.1	696.5	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550B3-425AXSP06	253.10	409.9	309.3	350.3	-	257.7	409.4	310.5	350.5	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550B3-432AXSP08	246.40	392.1	297.5	336	-	247.9	390.1	296.7	334.2	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB550B3-525AXSP08	293.50	458.4	350.8	394.1	-	295.3	455.8	350.1	392.4	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550B3-532AXSP08	274.90	432.8	329.9	371.9	-	276.7	430.6	329.5	369.9	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550B3-625AXSP08	317.40	489.3	376.9	421.9	-	319.2	486.3	375.8	419.8	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550B3-632AXSP08	301.30	469.1	359.3	403.9	-	302.9	466.2	358.8	401.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550C2-425AXSP06	265.10	429	323.1	366.2	-	269.4	428.5	324.8	366.4	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550C2-432AXSP06	242.90	397.3	298.5	339.4	-	247.3	396.8	299.9	339.7	675.2	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550C2-525AXSP06	295.80	475.2	360.2	407.1	800	300.8	474.4	361.7	407.1	790.7	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB550C2-532AXSP08	287.50	453.6	345.2	388.8	-	289.2	450.4	344.6	387.2	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550C2-625AXSP08	335.40	518	398.5	446.3	-	337	514.3	397.4	443.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550C2-632AXSP08	316.40	493.7	378.1	424.7	-	318	490.4	376.9	422.4	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550C2-425AXSP06	265.10	429	323.1	366.2	-	269.4	428.5	324.8	366.4	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550C3-432AXSP06	242.90	397.3	298.5	339.4	-	247.3	396.8	299.9	339.7	675.2	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550C3-525AXSP06	295.80	475.2	360.2	407.1	800	300.8	474.4	361.7	407.1	790.7	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB550C3-532AXSP08	287.50	453.6	345.2	388.8	-	289.2	450.4	344.6	387.2	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550C3-625AXSP08	335.40	518	398.5	446.3	-	337	514.3	397.4	443.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550C3-632AXSP08	316.40	493.7	378.1	424.7	-	318	490.4	376.9	422.4	-	451	29.9	3"	361	19.8	3"	54		

EAW-VD1554ZB550K4-432AXSP08	246.80	392.8	298	336.6	-	248.8	390.9	297.8	335.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB550K4-525AXSP08	294.40	460	352	395.5	-	296.1	457.2	351.1	393.6	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K4-532AXSP08	275.40	434.2	330.5	372.5	-	277.1	431.3	330	370.5	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K4-625AXSP08	319.20	492.2	379.1	424.4	-	320.8	488.8	377.6	421.9	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K4-632AXSP08	302.30	470.7	361	405.2	-	303.7	467.6	359.9	403.1	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K5-425AXSP06	253.90	410.5	309.7	351.4	-	258.1	410.1	311.5	351.1	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550K5-432AXSP08	246.80	392.8	298	336.6	-	248.8	390.9	297.8	335.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB550K5-525AXSP08	294.40	460	352	395.5	-	296.1	457.2	351.1	393.6	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K5-532AXSP08	275.40	434.2	330.5	372.5	-	277.1	431.3	330	370.5	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K5-625AXSP08	319.20	492.2	379.1	424.4	-	320.8	488.8	377.6	421.9	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K5-632AXSP08	302.30	470.7	361	405.2	-	303.7	467.6	359.9	403.1	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K8-425AXSP06	253.90	410.5	309.7	351.4	-	258.1	410.1	311.5	351.1	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550K8-432AXSP08	246.80	392.8	298	336.6	-	248.8	390.9	297.8	335.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB550K8-525AXSP08	294.40	460	352	395.5	-	296.1	457.2	351.1	393.6	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K8-625AXSP08	319.20	492.2	379.1	424.4	-	320.8	488.8	377.6	421.9	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K8-632AXSP08	302.30	470.7	361	405.2	-	303.7	467.6	359.9	403.1	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K9-425AXSP06	253.90	410.5	309.7	351.4	-	258.1	410.1	311.5	351.1	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550K9-432AXSP08	246.80	392.8	298	336.6	-	248.8	390.9	297.8	335.4	-	304	27.8	3"	244	18.4	3"	365	39	3"
EAW-VD1554ZB550K9-525AXSP08	294.40	460	352	395.5	-	296.1	457.2	351.1	393.6	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K9-532AXSP08	275.40	434.2	330.5	372.5	-	277.1	431.3	330	370.5	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550K9-625AXSP08	319.20	492.2	379.1	424.4	-	320.8	488.8	377.6	421.9	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550K9-632AXSP08	302.30	470.7	361	405.2	-	303.7	467.6	359.9	403.1	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550R3-425AXSP06	260.80	421.7	318.4	360.7	-	265.3	421.6	319.8	361.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550R3-432AXSP06	239.80	392.3	295.1	335.2	673.3	244.4	392.1	296.5	335.1	666.9	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB550R3-525AXSP08	302.60	472.7	361.9	406.7	-	304	470.1	361.2	404.4	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550R3-532AXSP08	283.00	446.1	339.7	382.5	-	284.9	443.3	339.4	381.2	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB550R3-625AXSP08	327.90	506.1	389.5	436.1	-	329.8	503	388.4	434	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB550R3-632AXSP08	310.60	484.3	370.6	416.7	-	312.3	481.3	370.1	414.1	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C2-425AXSP06	283.80	460.1	346.5	392.6	-	288.6	459.6	347.9	393.6	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C2-432AXSP06	260.80	426.2	319.9	364	-	265.7	426.4	321.8	364.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C2-525AXSP06	317.20	509.2	386.2	436.2	-	322.8	509.3	387.9	436.4	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C2-532AXSP06	295.00	479.4	361.2	409.7	815.3	300.6	479.2	363.4	410.3	807.1	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C2-625AXSP08	358.50	555.1	426.2	477.7	-	360.4	552.1	425.3	475.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C2-632AXSP08	338.30	528.9	404.7	455	-	340.7	526.3	404.2	453.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C3-425AXSP06	283.80	460.1	346.5	392.6	-	288.6	459.6	347.9	393.6	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C3-432AXSP06	260.80	426.2	319.9	364	-	265.7	426.4	321.8	364.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C3-525AXSP06	317.20	509.2	386.2	436.2	-	322.8	509.3	387.9	436.4	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C3-532AXSP06	295.00	479.4	361.2	409.7	815.3	300.6	479.2	363.4	410.3	807.1	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C3-625AXSP08	358.50	555.1	426.2	477.7	-	360.4	552.1	425.3	475.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C3-632AXSP08	338.30	528.9	404.7	455	-	340.7	526.3	404.2	453.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C3-632AXSP06	283.80	460.1	346.5	392.6	-	288.6	459.6	347.9	393.6	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C4-425AXSP06	260.80	426.2	319.9	364	-	265.7	426.4	321.8	364.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C4-525AXSP06	317.20	509.2	386.2	436.2	-	322.8	509.3	387.9	436.4	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C4-532AXSP06	295.00	479.4	361.2	409.7	815.3	300.6	479.2	363.4	410.3	807.1	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C4-625AXSP08	358.50	555.1	426.2	477.7	-	360.4	552.1	425.3	475.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C4-632AXSP08	338.30	528.9	404.7	455	-	340.7	526.3	404.2	453.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C5-425AXSP06	283.80	460.1	346.5	392.6	-	288.6	459.6	347.9	393.6	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C5-432AXSP06	260.80	426.2	319.9	364	-	265.7	426.4	321.8	364.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C5-525AXSP06	317.20	509.2	386.2	436.2	-	322.8	509.3	387.9	436.4	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C5-532AXSP06	295.00	479.4	361.2	409.7	815.3	300.6	479.2	363.4	410.3	807.1	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C5-625AXSP08	358.50	555.1	426.2	477.7	-	360.4	552.1	425.3	475.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C5-632AXSP08	338.30	528.9	404.7	455	-	340.7	526.3	404.2	453.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C8-425AXSP06	283.80	460.1	346.5	392.6	-	288.6	459.6	347.9	393.6	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C8-432AXSP06	260.80	426.2	319.9	364	-	265.7	426.4	321.8	364.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C8-525AXSP06	317.20	509.2	386.2	436.2	-	322.8	509.3	387.9	436.4	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C8-532AXSP06	295.00	479.4	361.2	409.7	815.3	300.6	479.2	363.4	410.3	807.1	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C8-625AXSP08	358.50	555.1	426.2	477.7	-	360.4	552.1	425.3	475.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C8-632AXSP08	338.30	528.9	404.7	455	-	340.7	526.3	404.2	453.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C9-425AXSP06	283.80	460.1	346.5	392.6	-	288.6	459.6	347.9	393.6	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C9-432AXSP06	260.80	426.2	319.9	364	-	265.7	426.4	321.8	364.2	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750C9-525AXSP06	317.20	509.2	386.2	436.2	-	322.8	509.3	387.9	436.4	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C9-532AXSP06	295.00	479.4	361.2	409.7	815.3	300.6	479.2	363.4	410.3	807.1	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750C9-625AXSP08	358.50	555.1	426.2	477.7	-	360.4	552.1	425.3	475.6	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750C9-632AXSP08	338.30	528.9	404.7	455	-	340.7	526.3	404.2	453.3	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750K2-425AXSP06	274.80	444.4	335.2	380.2</															

EAW-VD1554ZB750R3-425AXSP06	269.20	435.4	328.2	372.1	-	273.6	434.8	329.9	372.3	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750R3-432AXSP06	247.50	404.3	304.1	345.2	-	252	404.5	305.9	346	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD1554ZB750R3-525AXSP06	299.10	479.9	364.2	411.7	808.4	304.5	479.8	365.6	411.6	800	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD1554ZB750R3-532AXSP08	291.50	459.7	350.2	394.5	-	293.3	457.9	349.6	392.8	-	372	28.7	3"	298	19	3"	446	40.3	3"
EAW-VD1554ZB750R3-625AXSP08	337.40	521.2	400.8	448.9	-	339.2	517.8	400	447.1	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZB750R3-632AXSP08	319.80	499.3	381.7	429.4	-	321.8	495.9	381.6	427	-	451	29.9	3"	361	19.8	3"	541	38.3	4"
EAW-VD1554ZK017G7-425AXSP04	321.00	550.2	407.6	467.2	960.4	333.6	553	413.7	470.8	953.8	609	16.6	4"	487	14	3"	730	23.4	4"
EAW-VD1554ZK017G7-432AXSP06	328.60	532.9	400.9	455	-	332.6	532.2	402.1	454.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK017G7-525AXSP06	408.40	650.6	493	556.9	-	412.5	648.1	494	555.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK017G7-532AXSP06	377.20	605.7	457.5	518.1	-	381.3	604.1	458.5	517.6	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK017G7-625AXSP06	445.40	702.7	535.8	603.6	-	450	700	535.8	601.3	-	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK017G7-632AXSP06	416.50	662.3	503	567.7	-	421	659.5	503.8	566.2	-	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK017G7-632AXSP06	251.50	401.5	304.5	343.9	676.8	254	399.8	304.6	343	667.9	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C2-432AXSP06	231.50	373.9	282.8	320	635	234.5	372.3	282.9	319.2	627.1	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C2-525AXSP08	290.30	448.4	344.8	386.1	-	290.5	443.9	342.4	383.1	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C2-532AXSP08	271.50	423.1	323.9	363.7	-	272.1	419.1	321.9	360.7	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C2-625AXSP08	313.90	478.9	370.8	413.9	-	314.1	473.9	368.4	410	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C2-632AXSP08	297.60	458.4	353.2	395.7	-	297.9	454.1	351	391.9	742.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C4-425AXSP06	251.50	401.5	304.5	343.9	676.8	254	399.8	304.6	343	667.9	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C4-432AXSP06	231.50	373.9	282.8	320	635	234.5	372.3	282.9	319.2	627.1	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C4-525AXSP08	290.30	448.4	344.8	386.1	-	290.5	443.9	342.4	383.1	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C4-532AXSP08	271.50	423.1	323.9	363.7	-	272.1	419.1	321.9	360.7	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C4-625AXSP08	313.90	478.9	370.8	413.9	-	314.1	473.9	368.4	410	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C4-632AXSP08	297.60	458.4	353.2	395.7	-	297.9	454.1	351	391.9	742.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C5-425AXSP06	251.50	401.5	304.5	343.9	676.8	254	399.8	304.6	343	667.9	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C5-432AXSP06	231.50	373.9	282.8	320	635	234.5	372.3	282.9	319.2	627.1	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C5-525AXSP08	290.30	448.4	344.8	386.1	-	290.5	443.9	342.4	383.1	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C5-532AXSP08	271.50	423.1	323.9	363.7	-	272.1	419.1	321.9	360.7	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C5-625AXSP08	313.90	478.9	370.8	413.9	-	314.1	473.9	368.4	410	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C5-632AXSP08	297.60	458.4	353.2	395.7	-	297.9	454.1	351	391.9	742.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C8-425AXSP06	251.50	401.5	304.5	343.9	676.8	254	399.8	304.6	343	667.9	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C8-432AXSP06	231.50	373.9	282.8	320	635	234.5	372.3	282.9	319.2	627.1	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370C8-525AXSP08	290.30	448.4	344.8	386.1	-	290.5	443.9	342.4	383.1	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C8-532AXSP08	271.50	423.1	323.9	363.7	-	272.1	419.1	321.9	360.7	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370C8-625AXSP08	313.90	478.9	370.8	413.9	-	314.1	473.9	368.4	410	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370C8-632AXSP08	297.60	458.4	353.2	395.7	-	297.9	454.1	351	391.9	742.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K2-425AXSP06	242.00	386.8	293.8	331.6	651.1	244.8	385.2	293.9	330.3	642.8	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370K2-432AXSP08	235.50	370.1	282.1	317.6	-	235.9	367.2	281	315.5	-	304	30.5	3"	244	20.2	3"	365	42.8	3"
EAW-VD1554ZK370K2-525AXSP08	278.90	430.2	331.2	370.6	-	279.1	426	328.9	367.4	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K2-532AXSP08	261.80	407.4	312.2	350.4	-	262	403.6	310.4	347.6	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K2-625AXSP08	301.10	458.7	355	396.2	745.7	301.1	453.9	352.7	392.9	733.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K2-632AXSP08	286.00	439.9	339.3	379.5	722.6	286	435.9	337.3	376.5	711	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K4-425AXSP06	242.00	386.8	293.8	331.6	651.1	244.8	385.2	293.9	330.3	642.8	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370K4-432AXSP08	235.50	370.1	282.1	317.6	-	235.9	367.2	281	315.5	-	304	30.5	3"	244	20.2	3"	365	42.8	3"
EAW-VD1554ZK370K4-525AXSP08	278.90	430.2	331.2	370.6	-	279.1	426	328.9	367.4	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K4-532AXSP08	261.80	407.4	312.2	350.4	-	262	403.6	310.4	347.6	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K4-625AXSP08	301.10	458.7	355	396.2	745.7	301.1	453.9	352.7	392.9	733.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K4-632AXSP08	286.00	439.9	339.3	379.5	722.6	286	435.9	337.3	376.5	711	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K5-425AXSP06	242.00	386.8	293.8	331.6	651.1	244.8	385.2	293.9	330.3	642.8	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370K5-432AXSP08	235.50	370.1	282.1	317.6	-	235.9	367.2	281	315.5	-	304	30.5	3"	244	20.2	3"	365	42.8	3"
EAW-VD1554ZK370K5-525AXSP08	278.90	430.2	331.2	370.6	-	279.1	426	328.9	367.4	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K5-532AXSP08	261.80	407.4	312.2	350.4	-	262	403.6	310.4	347.6	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K5-625AXSP08	301.10	458.7	355	396.2	745.7	301.1	453.9	352.7	392.9	733.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K5-632AXSP08	286.00	439.9	339.3	379.5	722.6	286	435.9	337.3	376.5	711	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K8-425AXSP06	242.00	386.8	293.8	331.6	651.1	244.8	385.2	293.9	330.3	642.8	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK370K8-432AXSP08	235.50	370.1	282.1	317.6	-	235.9	367.2	281	315.5	-	304	30.5	3"	244	20.2	3"	365	42.8	3"
EAW-VD1554ZK370K8-525AXSP08	278.90	430.2	331.2	370.6	-	279.1	426	328.9	367.4	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K8-532AXSP08	261.80	407.4	312.2	350.4	-	262	403.6	310.4	347.6	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK370K8-625AXSP08	301.10	458.7	355	396.2	745.7	301.1	453.9	352.7	392.9	733.1	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK370K8-632AXSP08	286.00	439.9	339.3	379.5	722.6	286	435.9	337.3	376.5	711	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK400B3-425AXSP06	245.40	392.5	297.5	336.4	661	248.3	390.4	297.7	335.1	651.8	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK400B3-432AXSP08	238.60	375.3	285.9	321.9	-	239.1	372.3	284.3	319.8	-	304	30.5	3"	244	20.2	3"	365	42.8	3"
EAW-VD1554ZK400B3-525AXSP08	282.90	436.4	335.4	376	-	283.1	432.3	333.7	372.8	-	372	31.4	3"	298	20.7	3"	446	44	3"
EAW-VD1554ZK400B3-532AXSP08	265.50	412.8	316.2	355.5	-	265.8	409.6	314.9	352.7	-	372	31.4	3"	298					

EAW-VD1554ZK5S083-632AXSP08	320.50	495	380.6	426.2	-	321.1	490.6	378.4	422.9	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0C2-425AXSP06	282.80	452.4	342.6	387.7	-	286.2	450.5	342.7	386.6	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C2-432AXSP06	260.00	419.3	316.5	358.4	-	263.3	418	317.1	357.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C2-525AXSP06	316.70	501.2	381.7	430.2	838.3	320.1	498.7	381.9	428.7	826.3	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C2-525AXSP06	294.00	471.7	357.8	404.1	795	298.1	469.2	358	402.6	783.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C2-625AXSP06	340.90	536.1	410.9	461.4	886.3	344.8	533.1	410.6	459.4	873.9	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK5S0C2-632AXSP08	336.00	519.9	399.2	447.3	-	336.4	514.9	397.3	444.1	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0C3-425AXSP06	282.80	452.4	342.6	387.7	-	286.2	450.5	342.7	386.6	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C3-432AXSP06	260.00	419.3	316.5	358.4	-	263.3	418	317.1	357.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C3-525AXSP06	316.70	501.2	381.7	430.2	838.3	320.1	498.7	381.9	428.7	826.3	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C3-532AXSP06	294.00	471.7	357.8	404.1	795	298.1	469.2	358	402.6	783.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C3-625AXSP06	340.90	536.1	410.9	461.4	886.3	344.8	533.1	410.6	459.4	873.9	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK5S0C4-425AXSP06	282.80	452.4	342.6	387.7	-	286.2	450.5	342.7	386.6	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C4-432AXSP06	260.00	419.3	316.5	358.4	-	263.3	418	317.1	357.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C4-525AXSP06	316.70	501.2	381.7	430.2	838.3	320.1	498.7	381.9	428.7	826.3	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C4-532AXSP06	294.00	471.7	357.8	404.1	795	298.1	469.2	358	402.6	783.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C4-625AXSP06	340.90	536.1	410.9	461.4	886.3	344.8	533.1	410.6	459.4	873.9	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK5S0C4-632AXSP08	336.00	519.9	399.2	447.3	-	336.4	514.9	397.3	444.1	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0C5-425AXSP06	282.80	452.4	342.6	387.7	-	286.2	450.5	342.7	386.6	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C5-432AXSP06	260.00	419.3	316.5	358.4	-	263.3	418	317.1	357.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C5-525AXSP06	316.70	501.2	381.7	430.2	838.3	320.1	498.7	381.9	428.7	826.3	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C5-532AXSP06	294.00	471.7	357.8	404.1	795	298.1	469.2	358	402.6	783.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C5-625AXSP06	340.90	536.1	410.9	461.4	886.3	344.8	533.1	410.6	459.4	873.9	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK5S0C5-632AXSP08	336.00	519.9	399.2	447.3	-	336.4	514.9	397.3	444.1	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0C8-425AXSP06	282.80	452.4	342.6	387.7	-	286.2	450.5	342.7	386.6	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C8-432AXSP06	260.00	419.3	316.5	358.4	-	263.3	418	317.1	357.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C8-525AXSP06	316.70	501.2	381.7	430.2	838.3	320.1	498.7	381.9	428.7	826.3	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C8-532AXSP06	294.00	471.7	357.8	404.1	795	298.1	469.2	358	402.6	783.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C8-625AXSP06	340.90	536.1	410.9	461.4	886.3	344.8	533.1	410.6	459.4	873.9	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK5S0C8-632AXSP08	336.00	519.9	399.2	447.3	-	336.4	514.9	397.3	444.1	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0C9-425AXSP06	282.80	452.4	342.6	387.7	-	286.2	450.5	342.7	386.6	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C9-432AXSP06	260.00	419.3	316.5	358.4	-	263.3	418	317.1	357.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0C9-525AXSP06	316.70	501.2	381.7	430.2	838.3	320.1	498.7	381.9	428.7	826.3	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C9-625AXSP06	294.00	471.7	357.8	404.1	795	298.1	469.2	358	402.6	783.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0C9-632AXSP08	336.00	519.9	399.2	447.3	-	336.4	514.9	397.3	444.1	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K2-425AXSP06	272.00	434	329.2	371.6	-	274.8	432.3	329.3	370.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K2-432AXSP06	250.50	404.3	305.2	345.4	-	253.7	402.6	305.4	345.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K2-525AXSP06	302.30	478.8	365.2	410.7	798.6	305.6	476.6	365	409.5	788.7	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K2-532AXSP06	282.00	452.1	342.9	387.6	760.8	285.5	449.9	343.2	386.3	750.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K2-625AXSP08	339.10	518.4	400.7	447.6	-	339.2	513.6	398.1	443.8	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K2-632AXSP08	321.10	496	381.4	427.6	-	321.6	491.5	379.6	424.2	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K3-425AXSP06	272.00	434	329.2	371.6	-	274.8	432.3	329.3	370.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K3-432AXSP06	250.50	404.3	305.2	345.4	-	253.7	402.6	305.4	345.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K3-525AXSP06	302.30	478.8	365.2	410.7	798.6	305.6	476.6	365	409.5	788.7	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K3-532AXSP06	282.00	452.1	342.9	387.6	760.8	285.5	449.9	343.2	386.3	750.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K3-625AXSP08	339.10	518.4	400.7	447.6	-	339.2	513.6	398.1	443.8	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K4-425AXSP06	272.00	434	329.2	371.6	-	274.8	432.3	329.3	370.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K4-432AXSP06	250.50	404.3	305.2	345.4	-	253.7	402.6	305.4	345.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K4-525AXSP06	302.30	478.8	365.2	410.7	798.6	305.6	476.6	365	409.5	788.7	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K4-532AXSP06	282.00	452.1	342.9	387.6	760.8	285.5	449.9	343.2	386.3	750.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K4-625AXSP08	339.10	518.4	400.7	447.6	-	339.2	513.6	398.1	443.8	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K4-632AXSP08	321.10	496	381.4	427.6	-	321.6	491.5	379.6	424.2	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K5-425AXSP06	272.00	434	329.2	371.6	-	274.8	432.3	329.3	370.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K5-432AXSP06	250.50	404.3	305.2	345.4	-	253.7	402.6	305.4	345.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K5-525AXSP06	302.30	478.8	365.2	410.7	798.6	305.6	476.6	365	409.5	788.7	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K5-532AXSP06	282.00	452.1	342.9	387.6	760.8	285.5	449.9	343.2	386.3	750.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K5-625AXSP08	339.10	518.4	400.7	447.6	-	339.2	513.6	398.1	443.8	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K5-632AXSP08	321.10	496	381.4	427.6	-	321.6	491.5	379.6	424.2	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K8-425AXSP06	272.00	434	329.2	371.6	-	274.8	432.3	329.3	370.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K8-432AXSP06	250.50	404.3	305.2	345.4	-	253.7	402.6	305.4	345.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK5S0K8-432AXSP06	302.30	478.8	365.2	410.7	798.6	305.6	476.6	365	409.5	788.7	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K8-532AXSP06	282.00	452.1	342.9	387.6	760.8	285.5	449.9	343.2	386.3	750.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK5S0K8-625AXSP08	339.10	518.4	400.7	447.6	-	339.2	513.6	398.1	443.8	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1554ZK5S0K8-632AXSP08	321.10	496	381.4	427.6	-	321.6	491.5	379.6	424.2	-	451	32.6	3"	361	21.5	3"	541		

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1554ZK750C5-625AXSP06	367.30	576.8	441.2	496.5	956.4	371.7	574.6	441.7	494.6	944.4	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750C5-632AXSP06	345.70	549.4	418.9	472.2	919.4	350	547.5	419	470.5	908.6	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750C8-425AXSP06	303.90	487.7	368.8	417.1	-	307.6	486.3	369.4	415.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750C8-432AXSP06	279.90	452	340.6	386.3	-	283.1	450.7	341.3	385.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750C8-525AXSP06	341.00	540.1	410.9	462.9	-	344.9	537.6	411.3	462.1	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750C8-532AXSP06	317.10	507.6	385.1	434.7	-	321	506.4	385.3	433.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750C8-625AXSP06	367.30	576.8	441.2	496.5	956.4	371.7	574.6	441.7	494.6	944.4	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750C8-632AXSP06	345.70	549.4	418.9	472.2	919.4	350	547.5	419	470.5	908.6	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750C9-425AXSP06	303.90	487.7	368.8	417.1	-	307.6	486.3	369.4	415.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750C9-432AXSP06	279.90	452	340.6	386.3	-	283.1	450.7	341.3	385.1	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750C9-525AXSP06	341.00	540.1	410.9	462.9	-	344.9	537.6	411.3	462.1	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750C9-532AXSP06	317.10	507.6	385.1	434.7	-	321	506.4	385.3	433.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750C9-625AXSP06	367.30	576.8	441.2	496.5	956.4	371.7	574.6	441.7	494.6	944.4	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750C9-632AXSP06	345.70	549.4	418.9	472.2	919.4	350	547.5	419	470.5	908.6	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K2-425AXSP06	294.50	471.4	356.4	403.6	-	298	470.2	357.7	402.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K2-432AXSP06	271.60	437.7	330.4	374.4	-	275.1	437.3	331	374	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K2-525AXSP06	329.20	520.5	396.5	447.1	-	332.9	518.8	396.8	445.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K2-532AXSP06	306.40	491	371.9	420.2	828.9	310.7	489.3	372.8	419.4	818.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K2-625AXSP06	353.50	555.1	425.1	478.1	919.6	357.5	552.7	425.3	476.1	906.8	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K2-632AXSP06	333.30	530.4	404.2	455.4	885.4	337.9	528.4	404.9	454.4	875	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K3-425AXSP06	294.50	471.4	356.4	403.6	-	298	470.2	357.7	402.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K3-432AXSP06	271.60	437.7	330.4	374.4	-	275.1	437.3	331	374	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K3-525AXSP06	329.20	520.5	396.5	447.1	-	332.9	518.8	396.8	445.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K3-532AXSP06	306.40	491	371.9	420.2	828.9	310.7	489.3	372.8	419.4	818.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K3-625AXSP06	353.50	555.1	425.1	478.1	919.6	357.5	552.7	425.3	476.1	906.8	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K3-632AXSP06	333.30	530.4	404.2	455.4	885.4	337.9	528.4	404.9	454.4	875	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K4-425AXSP06	294.50	471.4	356.4	403.6	-	298	470.2	357.7	402.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K4-432AXSP06	271.60	437.7	330.4	374.4	-	275.1	437.3	331	374	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K4-525AXSP06	329.20	520.5	396.5	447.1	-	332.9	518.8	396.8	445.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K4-532AXSP06	306.40	491	371.9	420.2	828.9	310.7	489.3	372.8	419.4	818.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K4-625AXSP06	353.50	555.1	425.1	478.1	919.6	357.5	552.7	425.3	476.1	906.8	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K4-632AXSP06	333.30	530.4	404.2	455.4	885.4	337.9	528.4	404.9	454.4	875	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K5-425AXSP06	294.50	471.4	356.4	403.6	-	298	470.2	357.7	402.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K5-432AXSP06	271.60	437.7	330.4	374.4	-	275.1	437.3	331	374	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K5-525AXSP06	329.20	520.5	396.5	447.1	-	332.9	518.8	396.8	445.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K5-532AXSP06	306.40	491	371.9	420.2	828.9	310.7	489.3	372.8	419.4	818.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K5-625AXSP06	353.50	555.1	425.1	478.1	919.6	357.5	552.7	425.3	476.1	906.8	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K5-632AXSP06	333.30	530.4	404.2	455.4	885.4	337.9	528.4	404.9	454.4	875	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K8-425AXSP06	294.50	471.4	356.4	403.6	-	298	470.2	357.7	402.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K8-432AXSP06	271.60	437.7	330.4	374.4	-	275.1	437.3	331	374	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K8-525AXSP06	329.20	520.5	396.5	447.1	-	332.9	518.8	396.8	445.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K8-532AXSP06	306.40	491	371.9	420.2	828.9	310.7	489.3	372.8	419.4	818.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K8-625AXSP06	353.50	555.1	425.1	478.1	919.6	357.5	552.7	425.3	476.1	906.8	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K8-632AXSP06	333.30	530.4	404.2	455.4	885.4	337.9	528.4	404.9	454.4	875	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K9-425AXSP06	294.50	471.4	356.4	403.6	-	298	470.2	357.7	402.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K9-432AXSP06	271.60	437.7	330.4	374.4	-	275.1	437.3	331	374	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750K9-525AXSP06	329.20	520.5	396.5	447.1	-	332.9	518.8	396.8	445.7	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K9-532AXSP06	306.40	491	371.9	420.2	828.9	310.7	489.3	372.8	419.4	818.5	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750K9-625AXSP06	353.50	555.1	425.1	478.1	919.6	357.5	552.7	425.3	476.1	906.8	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750K9-632AXSP06	333.30	530.4	404.2	455.4	885.4	337.9	528.4	404.9	454.4	875	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750R3-425AXSP06	288.40	461.1	348.9	395	-	291.8	459.9	350.1	394.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750R3-432AXSP06	266.20	429.5	323.9	366.9	-	269.8	428.2	324.5	366.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD1554ZK750R3-525AXSP06	321.40	509.1	387.6	436.9	-	325.5	506.7	387.8	435.5	841	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750R3-532AXSP06	300.00	480.2	364	411.8	810	303.6	478.5	364.8	411	800.9	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD1554ZK750R3-625AXSP06	344.80	541.7	415.1	466.8	895.9	349.2	539.4	415.3	464.7	884.4	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD1554ZK750R3-632AXSP08	340.50	527.4	405.3	454.2	-	341.5	523.1	403.4	451.1	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD1555PB370C2-425AXSP04	241.60	404.1	302	344.4	697.5	249.4	406.6	305.7	346.7	693.2	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD1555PB370C2-432AXSP06	242.10	388.5	293.3	332.1	-	244.5	387.7	294	331.3	-	293	25.6	3"	234	21.2	2"	352	35.9	3"
EAW-VD1555PB370C2-525AXSP06	294.50	462.8	353.1	397.8	-	297.2	461.4	353.3	396.5	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD1555PB370C2-532AXSP06	276.10	437.7	333	375.3	-	278.8	436.7	333.1	375	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD1555PB370C2-625AXSP06	317.00	492.4	377.9	423.9	-	319.9	490.7	378.4	423.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD1555PB370C2-632AXSP06	302.10	473.8	361.8	407.2	-	304.6	472	361.8	406.2	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD1555PB370C4-425AXSP04	241.60	404.1	302	344.4	697.5	249.4	406.6	305.7	346.7	693.2	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD1555PB370C4-432AXSP06	24																		

EAW-VD155SPB370K8-532AXSP06	266.10	421.5	320.7	361.8	-	268.9	420.4	320.6	360.8	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB370K8-625AXSP06	305.50	473.1	363.4	407.6	-	307.8	471.6	363.5	406.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB370K8-632AXSP06	290.30	455.1	348	391.5	-	293	453.3	348.4	390.4	748.7	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400B3-425AXSP04	234.30	392.6	293.8	334.9	677.6	241.9	395	297.3	337.1	672.5	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB400B3-432AXSP06	236.10	378.1	285.8	323.5	-	238.5	377.6	286.6	323.5	-	293	25.6	3"	331	21.2	2"	352	35.9	3"
EAW-VD155SPB400B3-525AXSP06	285.30	447.6	341.9	384.4	-	288.1	446.6	342.3	384	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400B3-532AXSP06	268.50	425.6	323.6	364.6	-	271	424	323.7	364.3	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400B3-625AXSP06	305.80	474.3	364.4	408.7	-	309.2	473.2	365.2	408.2	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400B3-632AXSP06	292.20	458.3	350.4	393.6	-	295.3	457	350.6	392.9	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400C3-425AXSP04	241.60	404.1	302	344.4	697.5	249.4	406.6	305.7	346.7	693.2	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB400C3-432AXSP06	242.10	388.5	293.3	332.1	-	244.5	387.7	294	331.3	-	293	25.6	3"	234	21.2	2"	352	35.9	3"
EAW-VD155SPB400C3-525AXSP06	294.50	462.8	353.1	397.8	-	297.2	461.4	353.3	396.5	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400C3-532AXSP06	276.10	437.7	333	375.3	-	278.8	436.7	333.1	375	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400C3-625AXSP06	317.00	492.4	377.9	423.9	-	319.9	490.7	378.4	423.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400C3-632AXSP06	302.10	473.8	361.8	407.2	-	304.6	472	361.8	406.2	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400C9-425AXSP04	241.60	404.1	302	344.4	697.5	249.4	406.6	305.7	346.7	693.2	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB400C9-432AXSP06	242.10	388.5	293.3	332.1	-	244.5	387.7	294	331.3	-	293	25.6	3"	234	21.2	2"	352	35.9	3"
EAW-VD155SPB400C9-525AXSP06	294.50	462.8	353.1	397.8	-	297.2	461.4	353.3	396.5	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400C9-532AXSP06	276.10	437.7	333	375.3	-	278.8	436.7	333.1	375	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400C9-625AXSP06	317.00	492.4	377.9	423.9	-	319.9	490.7	378.4	423.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400C9-632AXSP06	302.10	473.8	361.8	407.2	-	304.6	472	361.8	406.2	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400K3-425AXSP04	232.00	389.4	290.6	331.7	670.8	239.5	390.9	294.4	333.7	666.3	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB400K3-432AXSP06	233.60	374.3	283	320.3	-	235.9	373.4	283.6	319.5	-	293	25.6	3"	234	21.2	2"	352	35.9	3"
EAW-VD155SPB400K3-525AXSP06	283.30	445	339.5	382.2	-	285.7	443.5	340.1	381.4	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400K3-532AXSP06	266.10	421.5	320.7	361.8	-	268.9	420.4	320.6	360.8	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400K3-625AXSP06	305.50	473.1	363.4	407.6	-	307.8	471.6	363.5	406.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400K3-632AXSP06	290.30	455.1	348	391.5	-	293	453.3	348.4	390.4	748.7	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400K9-425AXSP04	232.00	389.4	290.6	331.7	670.8	239.5	390.9	294.4	333.7	666.3	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB400K9-432AXSP06	233.60	374.3	283	320.3	-	235.9	373.4	283.6	319.5	-	293	25.6	3"	234	21.2	2"	352	35.9	3"
EAW-VD155SPB400K9-525AXSP06	283.30	445	339.5	382.2	-	285.7	443.5	340.1	381.4	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400K9-532AXSP06	266.10	421.5	320.7	361.8	-	268.9	420.4	320.6	360.8	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400K9-625AXSP06	305.50	473.1	363.4	407.6	-	307.8	471.6	363.5	406.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400K9-632AXSP06	290.30	455.1	348	391.5	-	293	453.3	348.4	390.4	748.7	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400R3-425AXSP04	236.10	396.1	295.8	337.2	682.8	244	397.9	299.4	339.5	677.6	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB400R3-432AXSP06	237.60	381.1	287.7	326	-	240	380.4	288.2	325.3	-	293	25.6	3"	234	21.2	2"	352	35.9	3"
EAW-VD155SPB400R3-525AXSP06	287.70	452.3	344.9	388.4	-	290.4	451	345.6	387.7	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400R3-532AXSP06	270.30	428.7	325.9	367.8	-	272.9	427.8	326	366.9	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB400R3-625AXSP06	310.00	481	369.4	414.3	-	312.9	479.1	369.6	413.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB400R3-632AXSP06	295.20	462.5	353.5	397.7	-	298.1	460.8	354	396.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB50B3-425AXSP04	295.00	428.7	320.6	365.5	742.3	265.1	431.3	324.6	368	737.8	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB50B3-432AXSP04	236.20	399.4	297.4	339.8	696	244.3	402	301.4	342.4	692	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB50B3-525AXSP06	311.30	489.9	373.5	420.5	-	314.5	489.5	374.1	420.1	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB50B3-532AXSP06	292.20	464.3	352.3	398.2	-	295.7	464	353.6	397.9	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB50B3-625AXSP06	334.00	519.9	398.4	447.2	-	337.9	518.7	399.9	447.4	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB50B3-632AXSP06	319.00	500.9	382.4	430.6	-	322.5	500.2	383.3	430	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C2-425AXSP04	271.10	451.7	337.3	384.4	-	279.4	454.5	341.6	387.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C2-432AXSP04	247.80	418.3	311.5	356.1	730	256.1	420.9	315.4	358.4	725.4	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C2-525AXSP04	300.90	499.9	375.4	426.7	855.5	310.9	502.5	379.9	429.1	849.3	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550C2-532AXSP06	307.50	489.4	371.1	419.8	-	311.1	488.9	372.4	419.4	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550C2-625AXSP06	356.50	555.6	425.5	478.1	-	359.6	554.2	426.5	477.5	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C2-632AXSP06	337.90	531.5	405.5	456.3	-	340.9	530.4	406.2	456.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C3-425AXSP04	271.10	451.7	337.3	384.4	-	279.4	454.5	341.6	387.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C3-432AXSP04	247.80	418.3	311.5	356.1	730	256.1	420.9	315.4	358.4	725.4	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C3-432AXSP06	300.90	499.9	375.4	426.7	855.5	310.9	502.5	379.9	429.1	849.3	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550C3-532AXSP06	307.50	489.4	371.1	419.8	-	311.1	488.9	372.4	419.4	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550C3-625AXSP06	356.50	555.6	425.5	478.1	-	359.6	554.2	426.5	477.5	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C3-632AXSP06	337.90	531.5	405.5	456.3	-	340.9	530.4	406.2	456.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C4-425AXSP04	271.10	451.7	337.3	384.4	-	279.4	454.5	341.6	387.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C4-432AXSP04	247.80	418.3	311.5	356.1	730	256.1	420.9	315.4	358.4	725.4	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C4-525AXSP04	300.90	499.9	375.4	426.7	855.5	310.9	502.5	379.9	429.1	849.3	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550C4-532AXSP06	307.50	489.4	371.1	419.8	-	311.1	488.9	372.4	419.4	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550C4-625AXSP06	356.50	555.6	425.5	478.1	-	359.6	554.2	426.5	477.5	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C4-632AXSP06	337.90	531.5	405.5	456.3	-	340.9	530.4	406.2	456.1	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550C5-425AXSP04	271.10	451.7	337.3	384.4	-	279.4	454.5	341.6	387.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550C5-432AXSP04	247.80</																		

EAW-VD155SPB550K5-525AXSP04	285.60	475.2	356.4	405.5	811.7	295.4	477.5	361.2	408.3	806.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550K5-532AXSP06	294.30	467.6	354.8	400.3	-	297.1	466.4	355.3	399.9	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550K5-625AXSP06	339.00	527.3	404.4	454.1	-	342.3	525.7	405.1	453.3	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550K8-632AXSP06	321.50	506	386.1	434.3	-	325.2	504.7	386.6	433.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550K8-425AXSP04	258.60	431.6	322	367.1	746.2	266.6	434.2	326.5	370.2	741.4	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550K8-432AXSP04	237.00	401	298.5	341.2	699	245.1	403.4	302.4	343.6	694.7	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550K8-525AXSP04	285.60	475.2	356.4	405.5	811.7	295.4	477.5	361.2	408.3	806.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550K8-532AXSP06	294.30	467.6	354.8	400.3	-	297.1	466.4	355.3	399.9	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550K8-625AXSP06	339.00	527.3	404.4	454.1	-	342.3	525.7	405.1	453.3	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550K8-632AXSP06	321.50	506	386.1	434.3	-	325.2	504.7	386.6	433.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550K9-425AXSP04	258.60	431.6	322	367.1	746.2	266.6	434.2	326.5	370.2	741.4	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550K9-432AXSP04	237.00	401	298.5	341.2	699	245.1	403.4	302.4	343.6	694.7	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550K9-525AXSP04	285.60	475.2	356.4	405.5	811.7	295.4	477.5	361.2	408.3	806.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550K9-532AXSP06	294.30	467.6	354.8	400.3	-	297.1	466.4	355.3	399.9	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550K9-625AXSP06	339.00	527.3	404.4	454.1	-	342.3	525.7	405.1	453.3	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550K9-632AXSP06	321.50	506	386.1	434.3	-	325.2	504.7	386.6	433.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550R3-425AXSP04	264.80	442	330	376.5	-	273.3	445	334.2	379.1	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550R3-432AXSP04	243.30	410.8	305.6	349.5	715.9	251.2	413.5	309.9	352.3	711.8	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB550R3-525AXSP04	293.00	486.7	365.2	415.7	832.1	302.7	489.3	369.7	418.8	827.4	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB550R3-532AXSP06	300.90	478.2	363	409.8	-	304	478	363.8	409.5	-	372	26.6	3"	298	17.5	3"	446	37.3	3"
EAW-VD155SPB550R3-625AXSP06	346.80	540.6	414.4	465.4	-	350.3	539.3	414.8	464.2	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB550R3-632AXSP06	329.40	518.1	395.1	445.2	-	332.8	517.1	395.8	444.2	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750C2-425AXSP04	287.60	478.3	356.7	407.1	-	296.6	481.5	361.5	410.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C2-432AXSP04	263.40	443.7	329.7	377.1	-	272.1	447.3	334.3	380.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C2-525AXSP04	318.70	527.8	396	450.6	905.6	328.9	531	401.1	454.2	900.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C2-532AXSP04	296.20	497.1	371.2	423.8	860.3	306.4	500.6	376.6	426.9	855.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C2-625AXSP04	339.60	560.5	421.9	479.7	951.3	351.4	564	427.8	483.6	946.4	676	18.7	4"	541	12.3	4"	812	26.3	4"
EAW-VD155SPB750C2-632AXSP06	356.10	561.7	427.7	481.7	-	360.1	560.8	428.6	481.6	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750C3-425AXSP04	287.60	478.3	356.7	407.1	-	296.6	481.5	361.5	410.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C3-432AXSP04	263.40	443.7	329.7	377.1	-	272.1	447.3	334.3	380.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C3-525AXSP04	318.70	527.8	396	450.6	905.6	328.9	531	401.1	454.2	900.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C3-532AXSP04	296.20	497.1	371.2	423.8	860.3	306.4	500.6	376.6	426.9	855.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C3-625AXSP04	339.60	560.5	421.9	479.7	951.3	351.4	564	427.8	483.6	946.4	676	18.7	4"	541	12.3	4"	812	26.3	4"
EAW-VD155SPB750C3-632AXSP06	356.10	561.7	427.7	481.7	-	360.1	560.8	428.6	481.6	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750C4-425AXSP04	287.60	478.3	356.7	407.1	-	296.6	481.5	361.5	410.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C4-432AXSP04	263.40	443.7	329.7	377.1	-	272.1	447.3	334.3	380.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C4-525AXSP04	318.70	527.8	396	450.6	905.6	328.9	531	401.1	454.2	900.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C4-532AXSP04	296.20	497.1	371.2	423.8	860.3	306.4	500.6	376.6	426.9	855.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C4-625AXSP04	339.60	560.5	421.9	479.7	951.3	351.4	564	427.8	483.6	946.4	676	18.7	4"	541	12.3	4"	812	26.3	4"
EAW-VD155SPB750C4-632AXSP06	356.10	561.7	427.7	481.7	-	360.1	560.8	428.6	481.6	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750C5-425AXSP04	287.60	478.3	356.7	407.1	-	296.6	481.5	361.5	410.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C5-432AXSP04	263.40	443.7	329.7	377.1	-	272.1	447.3	334.3	380.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C5-525AXSP04	318.70	527.8	396	450.6	905.6	328.9	531	401.1	454.2	900.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C5-532AXSP04	296.20	497.1	371.2	423.8	860.3	306.4	500.6	376.6	426.9	855.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C5-625AXSP04	339.60	560.5	421.9	479.7	951.3	351.4	564	427.8	483.6	946.4	676	18.7	4"	541	12.3	4"	812	26.3	4"
EAW-VD155SPB750C5-632AXSP06	356.10	561.7	427.7	481.7	-	360.1	560.8	428.6	481.6	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750C8-425AXSP04	287.60	478.3	356.7	407.1	-	296.6	481.5	361.5	410.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C8-432AXSP04	263.40	443.7	329.7	377.1	-	272.1	447.3	334.3	380.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C8-525AXSP04	318.70	527.8	396	450.6	905.6	328.9	531	401.1	454.2	900.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C8-532AXSP04	296.20	497.1	371.2	423.8	860.3	306.4	500.6	376.6	426.9	855.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C8-625AXSP04	339.60	560.5	421.9	479.7	951.3	351.4	564	427.8	483.6	946.4	676	18.7	4"	541	12.3	4"	812	26.3	4"
EAW-VD155SPB750C8-632AXSP06	356.10	561.7	427.7	481.7	-	360.1	560.8	428.6	481.6	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750C9-425AXSP04	287.60	478.3	356.7	407.1	-	296.6	481.5	361.5	410.7	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C9-432AXSP04	263.40	443.7	329.7	377.1	-	272.1	447.3	334.3	380.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750C9-525AXSP04	318.70	527.8	396	450.6	905.6	328.9	531	401.1	454.2	900.8	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C9-532AXSP04	296.20	497.1	371.2	423.8	860.3	306.4	500.6	376.6	426.9	855.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750C9-625AXSP04	339.60	560.5	421.9	479.7	951.3	351.4	564	427.8	483.6	946.4	676	18.7	4"	541	12.3	4"	812	26.3	4"
EAW-VD155SPB750C9-632AXSP06	356.10	561.7	427.7	481.7	-	360.1	560.8	428.6	481.6	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750K2-425AXSP04	277.90	462.6	345	394.1	-	286.4	465.5	350	397.4	-	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750K2-432AXSP04	254.80	430.1	319.6	365.6	749.5	263.4	433.2	324.1	368.8	746.4	451	19.7	3"	361	13	3"	541	24.1	4"
EAW-VD155SPB750K2-525AXSP04	307.10	509.9	382.6	435	873.5	317.1	512.5	387.7	438.1	868.2	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750K2-532AXSP04	286.00	480.6	358.9	409.5	830.3	295.7	483.9	364	413.1	825.6	564	17.9	4"	451	14.3	3"	676	25.1	4"
EAW-VD155SPB750K2-625AXSP06	362.60	565.6	432.9	486.5	-	366.5	565.3	434.2	486.8	-	451	27.7	3"	361	18.3	3"	541	35.4	4"
EAW-VD155SPB750K2-632AXSP06	344.20	542	413.2	465.9	-	347.7													



EAW-VD155SP1370C2-432AXSP04	274.00	442.9	334.3	378.9	-	277.8	441.7	335	377.9	745.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370C2-525AXSP04	330.80	525.1	399.8	451.1	876.1	335.1	522.9	400.3	449.2	865.4	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370C2-532AXSP04	308.80	496.1	376.2	425.3	835.1	313.1	493.6	376.5	423.8	824.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370C2-625AXSP04	354.70	558.5	427.9	481	922.6	359.3	555.6	427.7	479.1	910.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370C2-632AXSP04	335.20	534.8	406.7	459.2	890.9	339.9	532.3	407.6	457.7	879.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370C4-425AXSP04	297.70	476	361	407.5	-	301.2	474.8	361.1	406.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370C4-432AXSP04	274.00	442.9	334.3	378.9	-	277.8	441.7	335	377.9	745.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370C4-525AXSP04	330.80	525.1	399.8	451.1	876.1	335.1	522.9	400.3	449.2	865.4	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370C4-532AXSP04	308.80	496.1	376.2	425.3	835.1	313.1	493.6	376.5	423.8	824.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370C4-625AXSP04	354.70	558.5	427.9	481	922.6	359.3	555.6	427.7	479.1	910.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370C4-632AXSP04	335.20	534.8	406.7	459.2	890.9	339.9	532.3	407.6	457.7	879.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370C5-425AXSP04	297.70	476	361	407.5	-	301.2	474.8	361.1	406.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370C5-432AXSP04	274.00	442.9	334.3	378.9	-	277.8	441.7	335	377.9	745.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370C5-525AXSP04	330.80	525.1	399.8	451.1	876.1	335.1	522.9	400.3	449.2	865.4	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370C5-532AXSP04	308.80	496.1	376.2	425.3	835.1	313.1	493.6	376.5	423.8	824.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370C5-625AXSP04	354.70	558.5	427.9	481	922.6	359.3	555.6	427.7	479.1	910.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370C5-632AXSP04	335.20	534.8	406.7	459.2	890.9	339.9	532.3	407.6	457.7	879.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K2-425AXSP04	286.40	458.5	347.1	392.3	-	289.8	456.6	347.8	391.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K2-432AXSP04	264.20	427.5	322.6	365.5	726.6	267.8	426.4	323.3	365.1	718.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K2-525AXSP04	317.50	503.7	384	432.4	839.5	321.5	501.5	384.4	431.1	829.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K2-532AXSP04	296.40	476.8	361.5	409.1	801.6	301	475.1	362.4	407.7	791.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K2-625AXSP04	339.40	535	409.8	461	882	344.2	532.1	409.6	459.2	870	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K2-632AXSP04	321.30	513.1	390.2	440.9	853.9	326.2	510.7	390.9	439.4	842.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K4-425AXSP04	286.40	458.5	347.1	392.3	-	289.8	456.6	347.8	391.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K4-432AXSP04	264.20	427.5	322.6	365.5	726.6	267.8	426.4	323.3	365.1	718.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K4-525AXSP04	317.50	503.7	384	432.4	839.5	321.5	501.5	384.4	431.1	829.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K4-532AXSP04	296.40	476.8	361.5	409.1	801.6	301	475.1	362.4	407.7	791.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K4-625AXSP04	339.40	535	409.8	461	882	344.2	532.1	409.6	459.2	870	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K4-632AXSP04	321.30	513.1	390.2	440.9	853.9	326.2	510.7	390.9	439.4	842.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K5-425AXSP04	286.40	458.5	347.1	392.3	-	289.8	456.6	347.8	391.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K5-432AXSP04	264.20	427.5	322.6	365.5	726.6	267.8	426.4	323.3	365.1	718.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K5-525AXSP04	317.50	503.7	384	432.4	839.5	321.5	501.5	384.4	431.1	829.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K5-532AXSP04	296.40	476.8	361.5	409.1	801.6	301	475.1	362.4	407.7	791.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K5-625AXSP04	339.40	535	409.8	461	882	344.2	532.1	409.6	459.2	870	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K5-632AXSP04	321.30	513.1	390.2	440.9	853.9	326.2	510.7	390.9	439.4	842.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K8-425AXSP04	286.40	458.5	347.1	392.3	-	289.8	456.6	347.8	391.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K8-432AXSP04	264.20	427.5	322.6	365.5	726.6	267.8	426.4	323.3	365.1	718.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155SP1370K8-525AXSP04	317.50	503.7	384	432.4	839.5	321.5	501.5	384.4	431.1	829.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K8-532AXSP04	296.40	476.8	361.5	409.1	801.6	301	475.1	362.4	407.7	791.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155SP1370K8-625AXSP04	339.40	535	409.8	461	882	344.2	532.1	409.6	459.2	870	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155SP1370K8-632AXSP04	321.30	513.1	390.2	440.9	853.9	326.2	510.7	390.9	439.4	842.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400B3-425AXSP04	290.20	464.1	351.7	397.6	-	294.2	463.1	352.5	396.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400B3-432AXSP04	267.70	432.7	326.9	370.4	737.1	271.3	431.7	327.7	369.6	729.1	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400B3-525AXSP04	321.50	510.5	389.6	438.7	852.1	325.8	508.5	389.6	437	841	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400B3-532AXSP04	300.80	483.4	366.9	414.6	813	305.1	481.8	367.3	413.3	803.4	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400B3-625AXSP04	343.30	541.4	414.6	466.5	892.7	348.5	539	414.7	465	881.3	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400B3-632AXSP04	325.90	520	395.9	446.8	865.7	331	517.7	396.2	445.4	855.1	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400C3-425AXSP04	297.70	476	361	407.5	-	301.2	474.8	361.1	406.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400C3-432AXSP04	274.00	442.9	334.3	378.9	-	277.8	441.7	335	377.9	745.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400C3-525AXSP04	330.80	525.1	399.8	451.1	876.1	335.1	522.9	400.3	449.2	865.4	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400C3-532AXSP04	308.80	496.1	376.2	425.3	835.1	313.1	493.6	376.5	423.8	824.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400C3-625AXSP04	354.70	558.5	427.9	481	922.6	359.3	555.6	427.7	479.1	910.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400C3-632AXSP04	335.20	534.8	406.7	459.2	890.9	339.9	532.3	407.6	457.7	879.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400C9-425AXSP04	297.70	476	361	407.5	-	301.2	474.8	361.1	406.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400C9-432AXSP04	274.00	442.9	334.3	378.9	-	277.8	441.7	335	377.9	745.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400C9-525AXSP04	330.80	525.1	399.8	451.1	876.1	335.1	522.9	400.3	449.2	865.4	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400C9-532AXSP04	308.80	496.1	376.2	425.3	835.1	313.1	493.6	376.5	423.8	824.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400C9-625AXSP04	354.70	558.5	427.9	481	922.6	359.3	555.6	427.7	479.1	910.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400C9-632AXSP04	335.20	534.8	406.7	459.2	890.9	339.9	532.3	407.6	457.7	879.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD155PI400K3-425AXSP04	286.40	458.5	347.1	392.3	-	289.8	456.6	347.8	391.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400K3-432AXSP04	264.20	427.5	322.6	365.5	726.6	267.8	426.4	323.3	365.1	718.5	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD155PI400K3-525AXSP04	317.50	503.7	384	432.4	839.5	321.5	501.5	384.4	431.1	829.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD155PI400K3-532AXSP04	296.40	476.8	361.5	409.1	801.6	301	475.1	362.4	407.7	791.9	564	22.9	4"	451	17.6	3			

EAW-VD15SSPI50C4-425AXSP04	333.70	534.9	404.3	458.2	-	337.8	533.4	405	456.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C4-432AXSP04	306.80	495.5	373.9	423.3	-	310.7	495	374.7	422.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C4-525AXSP04	374.20	592.9	450.9	508.8	-	378.5	591.2	452.1	508.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C4-532AXSP04	347.60	557.8	422.3	477.6	-	352.5	555.7	423.3	476.6	932.3	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C4-625AXSP04	402.80	634.6	485.3	545.4	1052.4	408.1	631.9	485.7	543.9	1038.9	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C4-632AXSP04	379.40	604.2	459.7	518.3	1011.3	384.2	602.1	460.7	517.3	999.4	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C5-425AXSP04	333.70	534.9	404.3	458.2	-	337.8	533.4	405	456.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C5-432AXSP04	306.80	495.5	373.9	423.3	-	310.7	495	374.7	422.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C5-525AXSP04	374.20	592.9	450.9	508.8	-	378.5	591.2	452.1	508.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C5-532AXSP04	347.60	557.8	422.3	477.6	-	352.5	555.7	423.3	476.6	932.3	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C5-625AXSP04	402.80	634.6	485.3	545.4	1052.4	408.1	631.9	485.7	543.9	1038.9	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C5-632AXSP04	379.40	604.2	459.7	518.3	1011.3	384.2	602.1	460.7	517.3	999.4	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C8-425AXSP04	333.70	534.9	404.3	458.2	-	337.8	533.4	405	456.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C8-432AXSP04	306.80	495.5	373.9	423.3	-	310.7	495	374.7	422.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C8-525AXSP04	374.20	592.9	450.9	508.8	-	378.5	591.2	452.1	508.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C8-532AXSP04	347.60	557.8	422.3	477.6	-	352.5	555.7	423.3	476.6	932.3	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C8-625AXSP04	402.80	634.6	485.3	545.4	1052.4	408.1	631.9	485.7	543.9	1038.9	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C8-632AXSP04	379.40	604.2	459.7	518.3	1011.3	384.2	602.1	460.7	517.3	999.4	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C9-425AXSP04	333.70	534.9	404.3	458.2	-	337.8	533.4	405	456.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C9-432AXSP04	306.80	495.5	373.9	423.3	-	310.7	495	374.7	422.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50C9-525AXSP04	374.20	592.9	450.9	508.8	-	378.5	591.2	452.1	508.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C9-532AXSP04	347.60	557.8	422.3	477.6	-	352.5	555.7	423.3	476.6	932.3	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50C9-625AXSP04	402.80	634.6	485.3	545.4	1052.4	408.1	631.9	485.7	543.9	1038.9	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50C9-632AXSP04	379.40	604.2	459.7	518.3	1011.3	384.2	602.1	460.7	517.3	999.4	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K2-425AXSP04	320.10	512.5	388.1	438.7	-	324.1	511.3	388.9	438.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K2-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K2-525AXSP04	356.90	565.2	430.5	485.5	-	361	563.5	431	484	935.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K2-532AXSP04	332.50	533.8	404.3	457.6	901	337.2	532	405.3	456.7	891.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K2-625AXSP04	382.80	602.8	461.7	518.6	997.4	388	600.5	462.1	517.3	985	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K2-632AXSP04	361.50	576.1	439	494.7	962.8	366.5	574.1	439.2	493.7	950.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K3-425AXSP04	320.10	512.5	388.1	438.7	-	324.1	511.3	388.9	438.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K3-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K3-525AXSP04	356.90	565.2	430.5	485.5	-	361	563.5	431	484	935.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K3-532AXSP04	332.50	533.8	404.3	457.6	901	337.2	532	405.3	456.7	891.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K3-625AXSP04	382.80	602.8	461.7	518.6	997.4	388	600.5	462.1	517.3	985	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K3-632AXSP04	361.50	576.1	439	494.7	962.8	366.5	574.1	439.2	493.7	950.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K4-425AXSP04	320.10	512.5	388.1	438.7	-	324.1	511.3	388.9	438.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K4-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K4-525AXSP04	356.90	565.2	430.5	485.5	-	361	563.5	431	484	935.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K4-532AXSP04	332.50	533.8	404.3	457.6	901	337.2	532	405.3	456.7	891.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K4-625AXSP04	382.80	602.8	461.7	518.6	997.4	388	600.5	462.1	517.3	985	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K4-632AXSP04	361.50	576.1	439	494.7	962.8	366.5	574.1	439.2	493.7	950.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K5-425AXSP04	320.10	512.5	388.1	438.7	-	324.1	511.3	388.9	438.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K5-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K5-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K5-525AXSP04	356.90	565.2	430.5	485.5	-	361	563.5	431	484	935.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K5-532AXSP04	332.50	533.8	404.3	457.6	901	337.2	532	405.3	456.7	891.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K5-625AXSP04	382.80	602.8	461.7	518.6	997.4	388	600.5	462.1	517.3	985	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K5-632AXSP04	361.50	576.1	439	494.7	962.8	366.5	574.1	439.2	493.7	950.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K8-425AXSP04	320.10	512.5	388.1	438.7	-	324.1	511.3	388.9	438.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K8-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K8-525AXSP04	356.90	565.2	430.5	485.5	-	361	563.5	431	484	935.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K8-532AXSP04	332.50	533.8	404.3	457.6	901	337.2	532	405.3	456.7	891.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K8-625AXSP04	382.80	602.8	461.7	518.6	997.4	388	600.5	462.1	517.3	985	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K8-632AXSP04	361.50	576.1	439	494.7	962.8	366.5	574.1	439.2	493.7	950.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K9-425AXSP04	320.10	512.5	388.1	438.7	-	324.1	511.3	388.9	438.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K9-432AXSP04	295.30	476.3	359.5	407.4	-	299.5	475.9	360.3	407.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50K9-525AXSP04	356.90	565.2	430.5	485.5	-	361	563.5	431	484	935.7	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K9-532AXSP04	332.50	533.8	404.3	457.6	901	337.2	532	405.3	456.7	891.2	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50K9-625AXSP04	382.80	602.8	461.7	518.6	997.4	388	600.5	462.1	517.3	985	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50K9-632AXSP04	361.50	576.1	439	494.7	962.8	366.5	574.1	439.2	493.7	950.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSPI50R3-425AXSP04	328.80	526.5	398.2	450.4	-	332.5	525.5	399.3	450.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50R3-432AXSP04	303.10	489.9	369.3	418.7	-	307.2	488.9	370.3	417.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSPI50R3-525AXSP04	366.70	581.4	442.5	499.2	-	371.7	580	443.2	498.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSPI50R3-532AXSP04	342.10	548.3	415.5	469.7	926.5	346.6	546.7	416.8	469.1	916.7	564	22.9</							

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15SSP1750C9-632AXSP04	406.40	647.5	492.3	555.5	1086.1	412.4	645.5	493.5	554.6	1073.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K2-425AXSP04	345.10	554.6	419.3	474.6	-	350.1	554.1	420.8	474.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K2-432AXSP04	318.60	515.4	388.1	439.9	-	322.6	514.9	389	440.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K2-525AXSP04	386.70	612.9	466.3	525.6	-	391.2	611.9	467.5	525.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K2-532AXSP04	360.40	577.5	437.4	494.9	-	365.5	576.4	438.4	493.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K2-625AXSP04	415.20	653.1	499.7	561.8	1085.2	421	651.8	500.5	560.6	1072.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K2-632AXSP04	391.90	624.3	475.2	536	1046	397.5	622.9	476.1	534.9	1035	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K3-425AXSP04	345.10	554.6	419.3	474.6	-	350.1	554.1	420.8	474.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K3-432AXSP04	318.60	515.4	388.1	439.9	-	322.6	514.9	389	440.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K3-525AXSP04	386.70	612.9	466.3	525.6	-	391.2	611.9	467.5	525.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K3-532AXSP04	360.40	577.5	437.4	494.9	-	365.5	576.4	438.4	493.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K3-625AXSP04	415.20	653.1	499.7	561.8	1085.2	421	651.8	500.5	560.6	1072.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K3-632AXSP04	391.90	624.3	475.2	536	1046	397.5	622.9	476.1	534.9	1035	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K4-425AXSP04	345.10	554.6	419.3	474.6	-	350.1	554.1	420.8	474.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K4-432AXSP04	318.60	515.4	388.1	439.9	-	322.6	514.9	389	440.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K4-525AXSP04	386.70	612.9	466.3	525.6	-	391.2	611.9	467.5	525.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K4-532AXSP04	360.40	577.5	437.4	494.9	-	365.5	576.4	438.4	493.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K5-425AXSP04	345.10	554.6	419.3	474.6	-	350.1	554.1	420.8	474.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K5-432AXSP04	318.60	515.4	388.1	439.9	-	322.6	514.9	389	440.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K5-525AXSP04	386.70	612.9	466.3	525.6	-	391.2	611.9	467.5	525.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K5-625AXSP04	415.20	653.1	499.7	561.8	1085.2	421	651.8	500.5	560.6	1072.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K5-632AXSP04	391.90	624.3	475.2	536	1046	397.5	622.9	476.1	534.9	1035	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K8-425AXSP04	345.10	554.6	419.3	474.6	-	350.1	554.1	420.8	474.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K8-432AXSP04	318.60	515.4	388.1	439.9	-	322.6	514.9	389	440.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K8-525AXSP04	386.70	612.9	466.3	525.6	-	391.2	611.9	467.5	525.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K8-532AXSP04	360.40	577.5	437.4	494.9	-	365.5	576.4	438.4	493.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K8-625AXSP04	415.20	653.1	499.7	561.8	1085.2	421	651.8	500.5	560.6	1072.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K8-632AXSP04	391.90	624.3	475.2	536	1046	397.5	622.9	476.1	534.9	1035	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K9-425AXSP04	345.10	554.6	419.3	474.6	-	350.1	554.1	420.8	474.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K9-432AXSP04	318.60	515.4	388.1	439.9	-	322.6	514.9	389	440.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750K9-525AXSP04	386.70	612.9	466.3	525.6	-	391.2	611.9	467.5	525.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750K9-625AXSP04	415.20	653.1	499.7	561.8	1085.2	421	651.8	500.5	560.6	1072.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750K9-632AXSP04	391.90	624.3	475.2	536	1046	397.5	622.9	476.1	534.9	1035	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750R3-425AXSP04	338.00	543.4	410.4	464.4	-	342.8	541.9	411.9	464.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750R3-432AXSP04	312.20	504.8	380.1	431.1	-	316.4	504.2	381.3	431.3	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD15SSP1750R3-525AXSP04	378.10	599.4	455.7	514.3	-	383	597.6	456.8	513.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750R3-532AXSP04	352.90	565.6	428.1	484.2	-	357.8	564.4	429	483.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD15SSP1750R3-625AXSP04	405.30	637	487.7	548.2	1057.9	410.9	635.6	488.4	547.7	1046.3	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP1750R3-632AXSP04	383.20	610.6	464.5	523.8	1022.3	388.6	608.4	466	523.4	1010.3	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD15SSP3K70C2-425AXSP04	262.70	431	324.2	368.3	737.7	268.7	432	326.5	369.2	731.7	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C2-432AXSP04	241.30	401	300.5	341.6	691.9	247.5	402	302.8	343.2	685.8	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C2-525AXSP04	291.10	474.8	358.4	406.5	803.1	298.4	475.6	361.2	407.4	795.4	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD15SSP3K70C2-532AXSP06	295.80	465.3	354.5	399	-	297.4	462.6	353.7	397.2	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD15SSP3K70C2-625AXSP06	340.70	524	404	452.3	-	342.4	521.2	403.1	449.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C2-632AXSP06	323.90	503.1	385.7	433	-	325.4	500.5	385.1	431.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C4-425AXSP04	262.70	431	324.2	368.3	737.7	268.7	432	326.5	369.2	731.7	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C4-432AXSP04	241.30	401	300.5	341.6	691.9	247.5	402	302.8	343.2	685.8	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C4-525AXSP04	291.10	474.8	358.4	406.5	803.1	298.4	475.6	361.2	407.4	795.4	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD15SSP3K70C4-532AXSP06	295.80	465.3	354.5	399	-	297.4	462.6	353.7	397.2	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD15SSP3K70C4-625AXSP06	340.70	524	404	452.3	-	342.4	521.2	403.1	449.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C4-632AXSP06	323.90	503.1	385.7	433	-	325.4	500.5	385.1	431.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C5-425AXSP04	262.70	431	324.2	368.3	737.7	268.7	432	326.5	369.2	731.7	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C5-432AXSP04	241.30	401	300.5	341.6	691.9	247.5	402	302.8	343.2	685.8	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C5-525AXSP04	291.10	474.8	358.4	406.5	803.1	298.4	475.6	361.2	407.4	795.4	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD15SSP3K70C5-532AXSP06	295.80	465.3	354.5	399	-	297.4	462.6	353.7	397.2	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD15SSP3K70C5-625AXSP06	340.70	524	404	452.3	-	342.4	521.2	403.1	449.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C5-632AXSP06	323.90	503.1	385.7	433	-	325.4	500.5	385.1	431.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C8-425AXSP04	262.70	431	324.2	368.3	737.7	268.7	432	326.5	369.2	731.7	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C8-432AXSP04	241.30	401	300.5	341.6	691.9	247.5	402	302.8	343.2	685.8	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD15SSP3K70C8-525AXSP04	291.10	474.8	358.4	406.5	803.1	298.4	475.6	361.2	407.4	795.4	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD15SSP3K70C8-532AXSP06	295.80	465.3	354.5	399	-	297.4	462.6	353.7	397.2	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD15SSP3K70C8-625AXSP06	340.70	524	404	452.3	-	342.4	521.2	403.1	449.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70C8-632AXSP06	323.90	503.1	385.7	433	-	325.4	500.5	385.1	431.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD15SSP3K70K2-425AXSP04	252.30	415.1	311.6	354.4	709.1	258.4	415.2	314.4	355.2										

EAW-VD155SPK400C3-625AXSP06	340.70	524	404	452.3	-	342.4	521.2	403.1	449.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400C3-632AXSP06	323.90	503.1	385.7	433	-	325.4	500.5	385.1	431.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400C9-623AXSP04	262.70	431	324.2	368.3	737.7	268.7	432	326.5	369.2	731.7	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400C9-432AXSP04	241.30	401	300.5	341.6	691.9	247.5	402	302.8	343.2	685.8	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400C9-525AXSP04	291.10	474.8	358.4	406.5	803.1	298.4	475.6	361.2	407.4	795.4	454	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK400C9-532AXSP06	295.80	465.3	354.5	399	-	297.4	462.6	353.7	397.2	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD155SPK400C9-625AXSP06	340.70	524	404	452.3	-	342.4	521.2	403.1	449.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400C9-632AXSP06	323.90	503.1	385.7	433	-	325.4	500.5	385.1	431.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400K3-425AXSP04	252.30	415.1	311.6	354.4	709.1	258.4	415.2	314.4	355.2	703.2	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400K3-432AXSP04	232.40	386.4	289.3	329.6	665.5	238.4	387.2	291.6	330.9	659.5	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400K3-525AXSP06	303.40	472.6	362	406.5	-	304.9	469.6	360.9	404.4	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD155SPK400K3-532AXSP06	284.80	447	341	384.3	-	286.2	445	340.8	382.5	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD155SPK400K3-623AXSP06	327.20	502.4	387.8	434	-	328.6	499.5	386.8	431.4	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400K3-632AXSP06	311.40	483.5	370.6	416.5	-	312.7	480.2	369.9	414.1	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400K9-623AXSP04	252.30	415.1	311.6	354.4	709.1	258.4	415.2	314.4	355.2	703.2	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400K9-432AXSP04	232.40	386.4	289.3	329.6	665.5	238.4	387.2	291.6	330.9	659.5	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400K9-525AXSP06	303.40	472.6	362	406.5	-	304.9	469.6	360.9	404.4	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD155SPK400K9-532AXSP06	284.80	447	341	384.3	-	286.2	445	340.8	382.5	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD155SPK400K9-623AXSP06	327.20	502.4	387.8	434	-	328.6	499.5	386.8	431.4	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400K9-632AXSP06	311.40	483.5	370.6	416.5	-	312.7	480.2	369.9	414.1	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400R3-425AXSP04	257.30	422.4	317.4	360.5	723.3	263.2	423.4	319.8	362.1	716.7	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400R3-432AXSP04	236.80	394.1	294.7	335.9	678.1	242.9	394.3	297.3	336.8	672.3	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK400R3-525AXSP04	284.30	463.8	350.4	397.4	784.1	291.4	464.7	353.2	398.8	776.6	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK400R3-532AXSP06	290.00	455.6	347.4	390.9	-	291.6	453.1	346.8	389.3	-	372	29	3"	298	19.2	3"	446	40.8	3"
EAW-VD155SPK400R3-623AXSP06	332.50	511.6	394.2	441.2	-	334.2	508.3	393.4	438.8	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK400R3-632AXSP06	316.70	492.1	377.6	423.7	-	318.2	489	376.4	421.6	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK5083-425AXSP04	280.50	459.9	345.4	392.2	-	286.9	460.9	348	393.9	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK5083-432AXSP04	258.00	428	319.9	364.6	738.6	264.3	429	322.8	366.2	733.2	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK5083-525AXSP04	310.10	505.2	381.6	432.7	856.6	318	507	384.8	434.3	849.5	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK5083-532AXSP04	289.40	478.3	359.4	408.6	817.6	297.4	479.2	362.4	410.1	811.1	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK5083-625AXSP06	360.70	556.6	428.6	480	-	363.3	554.2	428	478.5	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK5083-632AXSP06	343.60	536	410.2	460.8	-	345.9	533.4	410.2	459.1	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK50C2-425AXSP04	295.10	482.4	362	411.5	-	301.5	484.2	365.4	413.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C2-432AXSP04	270.10	447.2	334.3	380.9	-	276.5	448.2	337.3	382.7	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C2-525AXSP04	328.70	534.7	403.7	457.3	908.4	336.5	535.6	406.9	458.9	900.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C2-532AXSP04	305.20	502.7	378.1	429.6	861.4	313	504	381.1	430.8	853.6	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C2-625AXSP04	352.30	570.8	432.5	489.2	958.5	361.1	571.1	435.8	490.9	950	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C2-632AXSP04	331.20	544.3	409.9	465.5	922.7	340.6	544.9	413.6	467.5	914.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C3-425AXSP04	295.10	482.4	362	411.5	-	301.5	484.2	365.4	413.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C3-432AXSP04	270.10	447.2	334.3	380.9	-	276.5	448.2	337.3	382.7	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C3-525AXSP04	328.70	534.7	403.7	457.3	908.4	336.5	535.6	406.9	458.9	900.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C3-532AXSP04	305.20	502.7	378.1	429.6	861.4	313	504	381.1	430.8	853.6	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C3-625AXSP04	352.30	570.8	432.5	489.2	958.5	361.1	571.1	435.8	490.9	950	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C3-632AXSP04	331.20	544.3	409.9	465.5	922.7	340.6	544.9	413.6	467.5	914.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C4-425AXSP04	295.10	482.4	362	411.5	-	301.5	484.2	365.4	413.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C4-432AXSP04	270.10	447.2	334.3	380.9	-	276.5	448.2	337.3	382.7	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C4-525AXSP04	328.70	534.7	403.7	457.3	908.4	336.5	535.6	406.9	458.9	900.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C4-532AXSP04	305.20	502.7	378.1	429.6	861.4	313	504	381.1	430.8	853.6	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C4-625AXSP04	352.30	570.8	432.5	489.2	958.5	361.1	571.1	435.8	490.9	950	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C4-632AXSP04	331.20	544.3	409.9	465.5	922.7	340.6	544.9	413.6	467.5	914.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C5-425AXSP04	295.10	482.4	362	411.5	-	301.5	484.2	365.4	413.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C5-432AXSP04	270.10	447.2	334.3	380.9	-	276.5	448.2	337.3	382.7	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C5-525AXSP04	328.70	534.7	403.7	457.3	908.4	336.5	535.6	406.9	458.9	900.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C5-532AXSP04	305.20	502.7	378.1	429.6	861.4	313	504	381.1	430.8	853.6	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C5-625AXSP04	352.30	570.8	432.5	489.2	958.5	361.1	571.1	435.8	490.9	950	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C5-632AXSP04	331.20	544.3	409.9	465.5	922.7	340.6	544.9	413.6	467.5	914.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C8-425AXSP04	295.10	482.4	362	411.5	-	301.5	484.2	365.4	413.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C8-432AXSP04	270.10	447.2	334.3	380.9	-	276.5	448.2	337.3	382.7	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C8-525AXSP04	328.70	534.7	403.7	457.3	908.4	336.5	535.6	406.9	458.9	900.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C8-532AXSP04	305.20	502.7	378.1	429.6	861.4	313	504	381.1	430.8	853.6	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50C8-625AXSP04	352.30	570.8	432.5	489.2	958.5	361.1	571.1	435.8	490.9	950	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C8-632AXSP04	331.20	544.3	409.9	465.5	922.7	340.6	544.9	413.6	467.5	914.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50C9-425AXSP04	295.10	482.4	362	411.5	-	301.5	484.2	365.4	413.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50C9-432AXSP04	270.10	447.2	334.3	380.9	-	276.5	4												


EAW-VD155SPK50K9-532AXSP04	290.80	480.8	361.2	410.6	820.8	298.6	481.2	363.9	411.8	814.7	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50K9-625AXSP04	333.60	541.4	409.8	463.9	906.7	342.3	541.6	413.3	465.4	898.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50K9-632AXSP06	346.10	539.2	413.1	464.2	-	348.3	536.4	412.4	462.3	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK50R3-425AXSP04	289.30	473.1	355.4	403.9	-	295.7	475.1	358.2	405.7	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50R3-432AXSP04	265.50	440.2	328.8	374.8	-	271.8	441.3	331.9	376.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK50R3-525AXSP04	320.30	522	393.8	446.7	885.9	328	523.1	397.2	447.8	878.7	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50R3-532AXSP04	298.90	492.4	370	421	842.9	306.6	494.1	373.9	422.5	836.1	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK50R3-625AXSP04	342.60	555.1	420.3	476	931.4	351.2	556.2	424.3	477.8	923.5	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK50R3-632AXSP06	354.50	553	423.4	475.8	-	356.4	550.4	422.8	474.1	-	451	30.2	3"	361	19.9	3"	541	38.9	4"
EAW-VD155SPK750C2-425AXSP04	313.70	513.5	384.8	438	-	320.6	515.7	388.5	440	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-432AXSP04	288.10	476.3	355.9	405.7	-	295.1	478.3	359.1	407.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-525AXSP04	349.50	568	428.4	485.9	-	358	570	432	487.7	-	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-532AXSP04	325.10	534.3	401.4	456.6	917	333.1	536.8	405.4	458.8	910.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-625AXSP04	374.10	604.3	458.3	518.1	1017.9	383.2	606.7	462.2	520.3	1009.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-632AXSP04	352.40	577.5	435.2	493.9	981.2	362	579.2	440	496.3	973.9	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-425AXSP04	313.70	513.5	384.8	438	-	320.6	515.7	388.5	440	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-432AXSP04	288.10	476.3	355.9	405.7	-	295.1	478.3	359.1	407.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-525AXSP04	349.50	568	428.4	485.9	-	358	570	432	487.7	-	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-532AXSP04	325.10	534.3	401.4	456.6	917	333.1	536.8	405.4	458.8	910.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-625AXSP04	374.10	604.3	458.3	518.1	1017.9	383.2	606.7	462.2	520.3	1009.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-632AXSP04	352.40	577.5	435.2	493.9	981.2	362	579.2	440	496.3	973.9	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-425AXSP04	313.70	513.5	384.8	438	-	320.6	515.7	388.5	440	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-432AXSP04	288.10	476.3	355.9	405.7	-	295.1	478.3	359.1	407.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-525AXSP04	349.50	568	428.4	485.9	-	358	570	432	487.7	-	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-532AXSP04	325.10	534.3	401.4	456.6	917	333.1	536.8	405.4	458.8	910.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-625AXSP04	374.10	604.3	458.3	518.1	1017.9	383.2	606.7	462.2	520.3	1009.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-632AXSP04	352.40	577.5	435.2	493.9	981.2	362	579.2	440	496.3	973.9	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-425AXSP04	313.70	513.5	384.8	438	-	320.6	515.7	388.5	440	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-432AXSP04	288.10	476.3	355.9	405.7	-	295.1	478.3	359.1	407.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C2-525AXSP04	349.50	568	428.4	485.9	-	358	570	432	487.7	-	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-532AXSP04	325.10	534.3	401.4	456.6	917	333.1	536.8	405.4	458.8	910.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C2-625AXSP04	374.10	604.3	458.3	518.1	1017.9	383.2	606.7	462.2	520.3	1009.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C2-632AXSP04	352.40	577.5	435.2	493.9	981.2	362	579.2	440	496.3	973.9	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C8-425AXSP04	313.70	513.5	384.8	438	-	320.6	515.7	388.5	440	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C8-432AXSP04	288.10	476.3	355.9	405.7	-	295.1	478.3	359.1	407.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C8-525AXSP04	349.50	568	428.4	485.9	-	358	570	432	487.7	-	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C8-532AXSP04	325.10	534.3	401.4	456.6	917	333.1	536.8	405.4	458.8	910.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C8-625AXSP04	374.10	604.3	458.3	518.1	1017.9	383.2	606.7	462.2	520.3	1009.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C8-632AXSP04	352.40	577.5	435.2	493.9	981.2	362	579.2	440	496.3	973.9	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C9-425AXSP04	313.70	513.5	384.8	438	-	320.6	515.7	388.5	440	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C9-432AXSP04	288.10	476.3	355.9	405.7	-	295.1	478.3	359.1	407.4	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750C9-525AXSP04	349.50	568	428.4	485.9	-	358	570	432	487.7	-	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C9-532AXSP04	325.10	534.3	401.4	456.6	917	333.1	536.8	405.4	458.8	910.3	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750C9-625AXSP04	374.10	604.3	458.3	518.1	1017.9	383.2	606.7	462.2	520.3	1009.6	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750C9-632AXSP04	352.40	577.5	435.2	493.9	981.2	362	579.2	440	496.3	973.9	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K2-425AXSP04	278.80	461	344.8	392.7	-	285.7	462.8	348.1	394.6	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750K2-432AXSP04	278.80	461	344.8	392.7	-	285.7	462.8	348.1	394.6	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750K2-525AXSP04	336.80	547.8	413.1	468.3	931.5	344.8	549.6	417.2	470.7	924.7	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750K2-532AXSP04	313.70	516.6	388	441.1	885.1	321.7	518.3	392	443.4	878.9	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750K2-625AXSP04	359.90	582.8	442	499.3	979.3	369.4	583.9	445.9	501.7	971.8	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K2-632AXSP04	339.70	557.2	419.9	477	945.4	348.7	558.8	423.7	479.1	938.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K3-425AXSP04	303.60	496.9	372.4	423.6	-	310.4	499	375.9	426.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750K3-432AXSP04	278.80	461	344.8	392.7	-	285.7	462.8	348.1	394.6	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750K3-525AXSP04	336.80	547.8	413.1	468.3	931.5	344.8	549.6	417.2	470.7	924.7	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750K3-532AXSP04	313.70	516.6	388	441.1	885.1	321.7	518.3	392	443.4	878.9	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750K3-625AXSP04	359.90	582.8	442	499.3	979.3	369.4	583.9	445.9	501.7	971.8	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K3-632AXSP04	339.70	557.2	419.9	477	945.4	348.7	558.8	423.7	479.1	938.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K4-425AXSP04	303.60	496.9	372.4	423.6	-	310.4	499	375.9	426.2	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750K4-432AXSP04	278.80	461	344.8	392.7	-	285.7	462.8	348.1	394.6	-	451	21.4	3"	361	14.1	3"	541	26.5	4"
EAW-VD155SPK750K4-525AXSP04	336.80	547.8	413.1	468.3	931.5	344.8	549.6	417.2	470.7	924.7	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750K4-532AXSP04	313.70	516.6	388	441.1	885.1	321.7	518.3	392	443.4	878.9	564	19.5	4"	451	15.4	3"	676	27.4	4"
EAW-VD155SPK750K4-625AXSP04	359.90	582.8	442	499.3	979.3	369.4	583.9	445.9	501.7	971.8	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K4-632AXSP04	339.70	557.2	419.9	477	945.4	348.7	558.8	423.7	479.1	938.2	676	20.4	4"	541	13.4	4"	812	28.6	4"
EAW-VD155SPK750K5-425AXSP04	303.60	496.9	372.4	423.6															

EAW-VD155S2B370C5-525AXSP06	342.90	535.3	409.5	460.3	-	344.8	532.1	409.1	458.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370C5-532AXSP06	320.40	506.2	385.8	434.4	-	322.8	502.7	384.6	432	835.5	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370C5-625AXSP06	367.70	569.5	438.2	490.9	934.3	370	564.9	437.2	488.1	920.4	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370C5-632AXSP06	347.90	545	417.7	469.1	903.4	350.7	541.6	417.1	466.8	890.9	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370C8-425AXSP06	307.00	486	370	416.6	-	309.3	483	369.2	415.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370C8-432AXSP06	283.50	452.1	342.6	387.3	-	285.9	450	342.5	386.1	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370C8-525AXSP06	342.90	535.3	409.5	460.3	-	344.8	532.1	409.1	458.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370C8-532AXSP06	320.40	506.2	385.8	434.4	-	322.8	502.7	384.6	432	835.5	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370C8-625AXSP06	367.70	569.5	438.2	490.9	934.3	370	564.9	437.2	488.1	920.4	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370C8-632AXSP06	347.90	545	417.7	469.1	903.4	350.7	541.6	417.1	466.8	890.9	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K2-425AXSP06	295.90	467.4	355.7	401	-	298	465.3	355.6	399.2	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K2-432AXSP06	273.80	436.4	331.2	374.2	-	276	434.3	330.5	372.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K2-525AXSP06	328.90	513.4	393.2	441.8	-	331.2	510.3	392.8	439.7	839.7	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K2-532AXSP06	308.00	486.5	370.7	417.8	813.3	310.3	483.9	370.2	415.6	802.2	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K2-625AXSP06	352.20	544.8	420.2	470.5	893.1	354.3	541	418.6	467.2	879.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K2-632AXSP06	333.80	522.9	401.2	450.4	865.9	336.4	519.5	400	448	852.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K4-425AXSP06	295.90	467.4	355.7	401	-	298	465.3	355.6	399.2	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K4-432AXSP06	273.80	436.4	331.2	374.2	-	276	434.3	330.5	372.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K4-525AXSP06	328.90	513.4	393.2	441.8	-	331.2	510.3	392.8	439.7	839.7	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K4-532AXSP06	308.00	486.5	370.7	417.8	813.3	310.3	483.9	370.2	415.6	802.2	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K4-625AXSP06	352.20	544.8	420.2	470.5	893.1	354.3	541	418.6	467.2	879.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K4-632AXSP06	333.80	522.9	401.2	450.4	865.9	336.4	519.5	400	448	852.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K5-425AXSP06	295.90	467.4	355.7	401	-	298	465.3	355.6	399.2	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K5-432AXSP06	273.80	436.4	331.2	374.2	-	276	434.3	330.5	372.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K5-525AXSP06	328.90	513.4	393.2	441.8	-	331.2	510.3	392.8	439.7	839.7	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K5-532AXSP06	308.00	486.5	370.7	417.8	813.3	310.3	483.9	370.2	415.6	802.2	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K5-625AXSP06	352.20	544.8	420.2	470.5	893.1	354.3	541	418.6	467.2	879.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K5-632AXSP06	333.80	522.9	401.2	450.4	865.9	336.4	519.5	400	448	852.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K8-425AXSP06	295.90	467.4	355.7	401	-	298	465.3	355.6	399.2	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K8-432AXSP06	273.80	436.4	331.2	374.2	-	276	434.3	330.5	372.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B370K8-525AXSP06	328.90	513.4	393.2	441.8	-	331.2	510.3	392.8	439.7	839.7	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K8-532AXSP06	308.00	486.5	370.7	417.8	813.3	310.3	483.9	370.2	415.6	802.2	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B370K8-625AXSP06	352.20	544.8	420.2	470.5	893.1	354.3	541	418.6	467.2	879.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B370K8-632AXSP06	333.80	522.9	401.2	450.4	865.9	336.4	519.5	400	448	852.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400B3-425AXSP06	299.90	474	360.5	406.5	-	302.1	471.3	360.5	404.8	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400B3-432AXSP06	277.40	442.6	335.1	378.7	-	279.8	440.6	335.1	377.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400B3-525AXSP06	333.30	520.5	398.5	447.8	-	335.7	517.5	398.2	445.7	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400B3-532AXSP06	312.10	493.3	375.8	423.6	825	314.6	490.1	375.3	421.4	814	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400B3-625AXSP06	356.00	551.5	424.7	475.6	904.3	358.9	548.2	424	473.3	891.6	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400B3-632AXSP06	338.20	530.1	406.6	456.5	878.1	341	526.8	406	454.2	866	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400C3-425AXSP06	307.00	486	370	416.6	-	309.3	483	369.2	415.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400C3-432AXSP06	283.50	452.1	342.6	387.3	-	285.9	450	342.5	386.1	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400C3-525AXSP06	342.90	535.3	409.5	460.3	-	344.8	532.1	409.1	458.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400C3-532AXSP06	320.40	506.2	385.8	434.4	-	322.8	502.7	384.6	432	835.5	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400C3-625AXSP06	367.70	569.5	438.2	490.9	934.3	370	564.9	437.2	488.1	920.4	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400C3-632AXSP06	347.90	545	417.7	469.1	903.4	350.7	541.6	417.1	466.8	890.9	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400C9-425AXSP06	307.00	486	370	416.6	-	309.3	483	369.2	415.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400C9-432AXSP06	283.50	452.1	342.6	387.3	-	285.9	450	342.5	386.1	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400C9-525AXSP06	342.90	535.3	409.5	460.3	-	344.8	532.1	409.1	458.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400C9-532AXSP06	320.40	506.2	385.8	434.4	-	322.8	502.7	384.6	432	835.5	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400C9-625AXSP06	367.70	569.5	438.2	490.9	934.3	370	564.9	437.2	488.1	920.4	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400C9-632AXSP06	347.90	545	417.7	469.1	903.4	350.7	541.6	417.1	466.8	890.9	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400K3-425AXSP06	295.90	467.4	355.7	401	-	298	465.3	355.6	399.2	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400K3-432AXSP06	273.80	436.4	331.2	374.2	-	276	434.3	330.5	372.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400K3-525AXSP06	328.90	513.4	393.2	441.8	-	331.2	510.3	392.8	439.7	839.7	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400K3-532AXSP06	308.00	486.5	370.7	417.8	813.3	310.3	483.9	370.2	415.6	802.2	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400K3-625AXSP06	352.20	544.8	420.2	470.5	893.1	354.3	541	418.6	467.2	879.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400K3-632AXSP06	333.80	522.9	401.2	450.4	865.9	336.4	519.5	400	448	852.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155S2B400K9-425AXSP06	295.90	467.4	355.7	401	-	298	465.3	355.6	399.2	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400K9-432AXSP06	273.80	436.4	331.2	374.2	-	276	434.3	330.5	372.3	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155S2B400K9-525AXSP06	328.90	513.4	393.2	441.8	-	331.2	510.3	392.8	439.7	839.7	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400K9-532AXSP06	308.00	486.5	370.7	417.8	813.3	310.3	483.9	370.2	415.6	802.2	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155S2B400K9-625AXSP06	352.20	544.8	420.2	470.5	893.1	354.3	541	418.6	467.2	879.8	609	26.3	4"	487	20.4	3"	730	36.9	4"

EAW-VD1555ZB550C8-432AXSP06	316.60	507.3	383	434	-	319.5	504.7	383.6	432.4	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550C8-525AXSP06	385.90	605	462.3	520.5	-	388.7	602	461.8	517.9	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550C8-532AXSP06	360.00	569.7	433	488.3	-	362.7	566.4	432.9	486.3	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550C8-625AXSP06	416.80	646.7	496.7	557.1	-	419.5	642.9	495.5	553.8	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550C8-632AXSP06	393.60	616.3	471.2	530	-	396.2	613	470.4	527.2	1012.6	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550C9-425AXSP04	311.10	521.4	389.9	445	899.3	320.6	523.7	393.9	446.4	890.8	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD1555ZB550C9-432AXSP06	316.60	507.3	383	434	-	319.5	504.7	383.6	432.4	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550C9-525AXSP06	385.90	605	462.3	520.5	-	388.7	602	461.8	517.9	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550C9-532AXSP06	360.00	569.7	433	488.3	-	362.7	566.4	432.9	486.3	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550C9-625AXSP06	416.80	646.7	496.7	557.1	-	419.5	642.9	495.5	553.8	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550C9-632AXSP06	393.60	616.3	471.2	530	-	396.2	613	470.4	527.2	1012.6	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K2-425AXSP06	330.00	523.8	397.6	449	-	332.6	521.5	397.4	447.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K2-432AXSP06	305.00	487.6	368.9	416.9	-	307.4	485.3	368.8	415.5	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K2-525AXSP06	368.60	577.4	441.3	495.8	-	371.3	573.8	440.8	494.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K2-532AXSP06	344.80	545.2	415.1	467.9	-	347.5	542.3	414.6	466.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K2-625AXSP06	396.80	614.5	472.6	529.8	1011.9	399.3	611	471.4	526.7	997.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K2-632AXSP06	374.90	587.6	449.9	505.8	977	378	584.5	449.2	503.1	963.2	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K3-425AXSP06	330.00	523.8	397.6	449	-	332.6	521.5	397.4	447.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K3-432AXSP06	305.00	487.6	368.9	416.9	-	307.4	485.3	368.8	415.5	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K3-525AXSP06	368.60	577.4	441.3	495.8	-	371.3	573.8	440.8	494.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K3-532AXSP06	344.80	545.2	415.1	467.9	-	347.5	542.3	414.6	466.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K3-625AXSP06	396.80	614.5	472.6	529.8	1011.9	399.3	611	471.4	526.7	997.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K3-632AXSP06	374.90	587.6	449.9	505.8	977	378	584.5	449.2	503.1	963.2	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K4-425AXSP06	330.00	523.8	397.6	449	-	332.6	521.5	397.4	447.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K4-432AXSP06	305.00	487.6	368.9	416.9	-	307.4	485.3	368.8	415.5	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K4-525AXSP06	368.60	577.4	441.3	495.8	-	371.3	573.8	440.8	494.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K4-532AXSP06	344.80	545.2	415.1	467.9	-	347.5	542.3	414.6	466.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K4-625AXSP06	396.80	614.5	472.6	529.8	1011.9	399.3	611	471.4	526.7	997.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K4-632AXSP06	374.90	587.6	449.9	505.8	977	378	584.5	449.2	503.1	963.2	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K5-425AXSP06	330.00	523.8	397.6	449	-	332.6	521.5	397.4	447.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K5-432AXSP06	305.00	487.6	368.9	416.9	-	307.4	485.3	368.8	415.5	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K5-525AXSP06	368.60	577.4	441.3	495.8	-	371.3	573.8	440.8	494.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K5-532AXSP06	344.80	545.2	415.1	467.9	-	347.5	542.3	414.6	466.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K5-625AXSP06	396.80	614.5	472.6	529.8	1011.9	399.3	611	471.4	526.7	997.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K5-632AXSP06	374.90	587.6	449.9	505.8	977	378	584.5	449.2	503.1	963.2	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K8-425AXSP06	330.00	523.8	397.6	449	-	332.6	521.5	397.4	447.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K8-432AXSP06	305.00	487.6	368.9	416.9	-	307.4	485.3	368.8	415.5	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K8-525AXSP06	368.60	577.4	441.3	495.8	-	371.3	573.8	440.8	494.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K8-532AXSP06	344.80	545.2	415.1	467.9	-	347.5	542.3	414.6	466.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K8-625AXSP06	396.80	614.5	472.6	529.8	1011.9	399.3	611	471.4	526.7	997.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K8-632AXSP06	374.90	587.6	449.9	505.8	977	378	584.5	449.2	503.1	963.2	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K9-425AXSP06	330.00	523.8	397.6	449	-	332.6	521.5	397.4	447.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K9-432AXSP06	305.00	487.6	368.9	416.9	-	307.4	485.3	368.8	415.5	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550K9-525AXSP06	368.60	577.4	441.3	495.8	-	371.3	573.8	440.8	494.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K9-532AXSP06	344.80	545.2	415.1	467.9	-	347.5	542.3	414.6	466.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550K9-625AXSP06	396.80	614.5	472.6	529.8	1011.9	399.3	611	471.4	526.7	997.8	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550K9-632AXSP06	374.90	587.6	449.9	505.8	977	378	584.5	449.2	503.1	963.2	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550R3-425AXSP04	305.90	513.5	383.6	437.7	885	315.8	515.3	387.8	440.2	877.4	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD1555ZB550R3-432AXSP04	312.90	500.8	378.4	428.6	-	315.9	498.7	378.5	427.4	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD1555ZB550R3-525AXSP06	378.30	593.4	453.1	509.9	-	381.2	590.8	452.8	507.7	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550R3-532AXSP06	354.30	560.2	426.1	480.4	-	356.7	557.5	425.7	478.8	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB550R3-625AXSP06	407.60	631.8	485.5	544.4	-	410.6	628	484.8	541.8	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB550R3-632AXSP06	385.90	604.5	462.5	519.4	1004.6	388.6	600.8	462	517.6	992	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB750C2-425AXSP04	334.80	559.7	418.5	476.7	967.2	345	562.3	423	479.2	959.6	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD1555ZB750C2-432AXSP04	305.80	518.9	385.3	440.8	901.9	315.9	520.5	390.1	443.8	894	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD1555ZB750C2-525AXSP06	412.90	649.5	495.2	557.2	-	416.2	646.6	494.9	555.5	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB750C2-532AXSP06	384.90	610.7	464.4	523.5	-	388	608.3	463.7	522.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB750C2-625AXSP06	445.40	692.9	531.2	596.3	-	448.6	689.2	530.8	593.7	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB750C2-632AXSP06	420.90	661.2	504.4	567.9	-	424.6	657.9	504.5	565.8	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD1555ZB750C3-425AXSP04	334.80	559.7	418.5	476.7	967.2	345	562.3	423	479.2	959.6	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD1555ZB750C3-432AXSP04	305.80	518.9	385.3	440.8	901.9	315.9	520.5	390.1	443.8	894	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD1555ZB750C3-525AXSP06	412.90	649.5	495.2	557.2	-	416.2	646.6	494.9	555.5	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB750C3-532AXSP06	384.90	610.7	464.4	523.5	-	388	608.3	463.7	522.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD1555ZB750C3-625AXSP06	445.40	692.9	531.2	596.3	-	448.6	689.2												

EAW-VD155SZB750K4-425AXSP04	323.20	540.8	404.3	461	933	333.5	543.2	409.3	463.3	925.7	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD155SZB750K4-432AXSP06	328.80	527.3	398.1	450.6	-	331.9	525.5	398.6	449.8	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155SZB750K4-525AXSP06	398.50	625.8	477.7	538	-	401.4	623.6	477.9	536.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K4-532AXSP06	372.30	590.4	448.8	506.5	-	375.9	588	448.9	504.4	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K4-625AXSP06	429.60	666.3	511.3	573.7	-	432.6	663.8	511.1	572.2	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K4-632AXSP06	406.30	637.3	487.4	547.7	-	409.7	634.7	486.6	546.3	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K5-425AXSP04	323.20	540.8	404.3	461	933	333.5	543.2	409.3	463.3	925.7	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD155SZB750K5-432AXSP06	328.80	527.3	398.1	450.6	-	331.9	525.5	398.6	449.8	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155SZB750K5-525AXSP06	398.50	625.8	477.7	538	-	401.4	623.6	477.9	536.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K5-532AXSP06	372.30	590.4	448.8	506.5	-	375.9	588	448.9	504.4	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K5-625AXSP06	429.60	666.3	511.3	573.7	-	432.6	663.8	511.1	572.2	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K5-632AXSP06	406.30	637.3	487.4	547.7	-	409.7	634.7	486.6	546.3	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K8-425AXSP04	323.20	540.8	404.3	461	933	333.5	543.2	409.3	463.3	925.7	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD155SZB750K8-432AXSP06	328.80	527.3	398.1	450.6	-	331.9	525.5	398.6	449.8	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155SZB750K8-525AXSP06	398.50	625.8	477.7	538	-	401.4	623.6	477.9	536.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K8-532AXSP06	372.30	590.4	448.8	506.5	-	375.9	588	448.9	504.4	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K8-625AXSP06	429.60	666.3	511.3	573.7	-	432.6	663.8	511.1	572.2	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K8-632AXSP06	406.30	637.3	487.4	547.7	-	409.7	634.7	486.6	546.3	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K9-425AXSP04	323.20	540.8	404.3	461	933	333.5	543.2	409.3	463.3	925.7	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD155SZB750K9-432AXSP06	328.80	527.3	398.1	450.6	-	331.9	525.5	398.6	449.8	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155SZB750K9-525AXSP06	398.50	625.8	477.7	538	-	401.4	623.6	477.9	536.1	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K9-532AXSP06	372.30	590.4	448.8	506.5	-	375.9	588	448.9	504.4	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750K9-625AXSP06	429.60	666.3	511.3	573.7	-	432.6	663.8	511.1	572.2	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750K9-632AXSP06	406.30	637.3	487.4	547.7	-	409.7	634.7	486.6	546.3	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750R3-425AXSP04	316.10	529.9	396	451.3	913.2	326.1	531.4	400.7	454.3	906	609	18.3	4"	487	15.1	3"	730	25.7	4"
EAW-VD155SZB750R3-432AXSP06	322.50	516.4	390.3	441.5	-	325.4	514.5	390.7	440.6	-	406	27.2	3"	325	17.9	3"	487	38.1	3"
EAW-VD155SZB750R3-525AXSP06	389.60	612	466.8	525.6	-	393	608.9	466.9	523.7	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750R3-532AXSP06	365.10	577.3	439.2	495.5	-	367.9	574.9	439.2	494.2	-	507	28.9	3"	406	19.1	3"	609	35.9	4"
EAW-VD155SZB750R3-625AXSP06	419.30	650.6	499.7	560.4	-	422.8	647.3	499.4	558.2	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZB750R3-632AXSP06	397.30	623.3	476.4	535.9	-	401.1	619.9	476.2	533.7	-	609	26.3	4"	487	20.4	3"	730	36.9	4"
EAW-VD155SZK017G7-425AXSP04	431.40	706.8	529.8	602.5	-	440	708.6	533.4	604.3	-	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK017G7-432AXSP04	393.30	649.4	485.4	553.5	-	401.6	651.5	488.9	554.8	-	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK017G7-525AXSP04	487.00	791	595.4	675.9	-	496.2	790.9	599.2	677	-	755	21.2	4"	604	14	4"	906	26	(2) 4"
EAW-VD155SZK017G7-532AXSP04	447.30	735.7	551.7	628.1	-	456.9	736.7	555.5	629.1	1251	755	21.2	4"	604	14	4"	906	26	(2) 4"
EAW-VD155SZK017G7-625AXSP04	531.20	857.9	650.5	735.8	1447.4	542.7	857.4	654	735.6	1432.4	913	18.9	(2) 4"	730	15	4"	1096	26.6	(2) 4"
EAW-VD155SZK017G7-632AXSP04	493.60	808.2	610.1	691.7	1375.2	505.2	808.8	613.5	692.4	1361.3	913	18.9	(2) 4"	730	15	4"	1096	26.6	(2) 4"
EAW-VD155SZK370C2-425AXSP06	325.50	510.9	389.6	438.8	-	326.7	506.4	388.2	435.5	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C2-432AXSP06	300.60	475.8	361.9	407.7	-	301.9	472.1	360.5	405.2	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C2-525AXSP06	363.40	562.7	432.2	484.6	-	364.1	557.7	429.8	480.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C2-532AXSP06	339.90	531.2	406.8	456.7	-	341.2	526.9	404.9	453.5	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C2-625AXSP06	390.30	597.9	462.2	516.7	976	391.6	592.4	459.9	512.5	960.5	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C2-632AXSP06	369.80	573	440.8	493.9	943.2	370.9	567.7	438.1	489.9	928.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C4-425AXSP06	325.50	510.9	389.6	438.8	-	326.7	506.4	388.2	435.5	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C4-432AXSP06	300.60	475.8	361.9	407.7	-	301.9	472.1	360.5	405.2	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C4-525AXSP06	363.40	562.7	432.2	484.6	-	364.1	557.7	429.8	480.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C4-532AXSP06	339.90	531.2	406.8	456.7	-	341.2	526.9	404.9	453.5	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C4-625AXSP06	390.30	597.9	462.2	516.7	976	391.6	592.4	459.9	512.5	960.5	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C4-632AXSP06	369.80	573	440.8	493.9	943.2	370.9	567.7	438.1	489.9	928.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C5-425AXSP06	325.50	510.9	389.6	438.8	-	326.7	506.4	388.2	435.5	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C5-432AXSP06	300.60	475.8	361.9	407.7	-	301.9	472.1	360.5	405.2	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C5-525AXSP06	363.40	562.7	432.2	484.6	-	364.1	557.7	429.8	480.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C5-532AXSP06	339.90	531.2	406.8	456.7	-	341.2	526.9	404.9	453.5	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C5-625AXSP06	390.30	597.9	462.2	516.7	976	391.6	592.4	459.9	512.5	960.5	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C5-632AXSP06	369.80	573	440.8	493.9	943.2	370.9	567.7	438.1	489.9	928.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C8-425AXSP06	325.50	510.9	389.6	438.8	-	326.7	506.4	388.2	435.5	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C8-432AXSP06	300.60	475.8	361.9	407.7	-	301.9	472.1	360.5	405.2	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370C8-525AXSP06	363.40	562.7	432.2	484.6	-	364.1	557.7	429.8	480.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C8-532AXSP06	339.90	531.2	406.8	456.7	-	341.2	526.9	404.9	453.5	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370C8-625AXSP06	390.30	597.9	462.2	516.7	976	391.6	592.4	459.9	512.5	960.5	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370C8-632AXSP06	369.80	573	440.8	493.9	943.2	370.9	567.7	438.1	489.9	928.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK370K2-425AXSP06	314.10	492.1	375.7	422.3	-	314.7	487.8	374.4	419.8	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370K2-432AXSP06	290.60	459	349.6	394.3	-	291.8	456.1	348.2	391.8	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK370K2-525AXSP06	349.20	539.8	415.1	465.2	-	349.9	535.2	412.9	461.1	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK370K2-532AXSP06	327.30	511.3	391.4	439.9	-	328.6	507.3	389.7	437	837.1	507	31.4	3"	406	20.7	3"			

EAW-VD155SZK400C9-632AXSP06	369.80	573	440.8	493.9	943.2	370.9	567.7	438.1	489.9	928.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK400K3-425AXSP06	314.10	492.1	375.7	422.3	-	314.7	487.8	374.4	419.8	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK400K3-432AXSP06	290.60	459	349.6	394.3	-	291.8	456.1	348.2	391.8	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK400K3-525AXSP06	349.20	539.8	415.1	465.2	-	349.9	535.2	412.9	461.1	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK400K3-532AXSP06	327.30	511.3	391.4	439.9	-	328.6	507.3	389.7	437	837.1	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK400K3-625AXSP06	373.90	572.7	442.6	494.6	933.1	375	567.4	440.3	490.5	917.4	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK400K3-632AXSP06	354.90	549.9	422.9	473.7	904.3	356	544.9	421	470	889.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK400K9-425AXSP06	314.10	492.1	375.7	422.3	-	314.7	487.8	374.4	419.8	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK400K9-432AXSP06	290.60	459	349.6	394.3	-	291.8	456.1	348.2	391.8	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK400K9-525AXSP06	349.20	539.8	415.1	465.2	-	349.9	535.2	412.9	461.1	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK400K9-532AXSP06	327.30	511.3	391.4	439.9	-	328.6	507.3	389.7	437	837.1	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK400K9-625AXSP06	373.90	572.7	442.6	494.6	933.1	375	567.4	440.3	490.5	917.4	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK400K9-632AXSP06	354.90	549.9	422.9	473.7	904.3	356	544.9	421	470	889.8	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK400R3-425AXSP06	320.60	502.9	383.7	431.4	-	321.5	498.8	382.5	429.1	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK400R3-432AXSP06	296.70	469.2	357.1	402.3	-	298.1	465.9	356	399.9	-	406	29.7	3"	325	19.6	3"	487	41.6	3"
EAW-VD155SZK400R3-525AXSP06	356.40	551.4	423.8	475	-	357.3	546.9	421.7	471.7	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK400R3-532AXSP06	334.70	522.6	399.7	449.4	-	336.1	518.6	398.2	446.6	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK400R3-625AXSP06	381.80	585.2	452.1	505.3	953.9	383.1	579.4	450	501.3	938.1	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK400R3-632AXSP06	362.70	561.6	432.3	484.3	924.1	364	556.8	430	480.7	910.7	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK500B3-425AXSP04	321.00	528.8	397.4	451.4	902.4	328.5	528.5	399.9	452.1	891.9	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK500B3-432AXSP04	294.70	491.4	367.1	419.1	844.9	302.4	492.1	370.4	419.8	835.7	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK500B3-525AXSP06	390.90	607	465.3	522.1	-	392.4	602.7	463.5	519	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK500B3-532AXSP06	366.00	573.1	437.7	492.7	-	367.5	569.2	436.4	489.3	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK500B3-625AXSP06	420.70	644.9	497.8	556.8	-	421.6	639.9	495.4	553	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK500B3-632AXSP06	398.80	618	474.4	532	-	400.2	613.2	473	528.6	1006.1	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C2-425AXSP04	335.90	552.2	415.5	471.6	944.1	343.2	551.8	417.4	472.2	932.8	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C2-432AXSP04	307.10	511.5	382.7	436.5	879.8	314.8	511.9	385.3	437	871	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C2-525AXSP06	409.80	636.9	488.1	548	-	410.6	631.9	486.6	544.4	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C2-532AXSP06	382.50	599.4	457.7	514.8	-	383.4	595.2	456.3	511.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C2-625AXSP06	442.90	681.1	525	587.5	-	444.3	675.4	522.3	583.3	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C2-632AXSP06	418.10	649	498.3	559.1	-	419.3	643.7	495.9	555.1	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C3-425AXSP04	335.90	552.2	415.5	471.6	944.1	343.2	551.8	417.4	472.2	932.8	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C3-432AXSP04	307.10	511.5	382.7	436.5	879.8	314.8	511.9	385.3	437	871	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C3-525AXSP06	409.80	636.9	488.1	548	-	410.6	631.9	486.6	544.4	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C3-532AXSP06	382.50	599.4	457.7	514.8	-	383.4	595.2	456.3	511.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C3-625AXSP06	442.90	681.1	525	587.5	-	444.3	675.4	522.3	583.3	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C3-632AXSP06	418.10	649	498.3	559.1	-	419.3	643.7	495.9	555.1	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C4-425AXSP04	335.90	552.2	415.5	471.6	944.1	343.2	551.8	417.4	472.2	932.8	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C4-432AXSP04	307.10	511.5	382.7	436.5	879.8	314.8	511.9	385.3	437	871	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C4-525AXSP06	409.80	636.9	488.1	548	-	410.6	631.9	486.6	544.4	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C4-532AXSP06	382.50	599.4	457.7	514.8	-	383.4	595.2	456.3	511.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C4-625AXSP06	442.90	681.1	525	587.5	-	444.3	675.4	522.3	583.3	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C4-632AXSP06	418.10	649	498.3	559.1	-	419.3	643.7	495.9	555.1	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C5-425AXSP04	335.90	552.2	415.5	471.6	944.1	343.2	551.8	417.4	472.2	932.8	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C5-432AXSP04	307.10	511.5	382.7	436.5	879.8	314.8	511.9	385.3	437	871	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C5-525AXSP06	409.80	636.9	488.1	548	-	410.6	631.9	486.6	544.4	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C5-532AXSP06	382.50	599.4	457.7	514.8	-	383.4	595.2	456.3	511.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C5-625AXSP06	442.90	681.1	525	587.5	-	444.3	675.4	522.3	583.3	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C5-632AXSP06	418.10	649	498.3	559.1	-	419.3	643.7	495.9	555.1	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C8-425AXSP04	335.90	552.2	415.5	471.6	944.1	343.2	551.8	417.4	472.2	932.8	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C8-432AXSP04	307.10	511.5	382.7	436.5	879.8	314.8	511.9	385.3	437	871	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C8-525AXSP06	409.80	636.9	488.1	548	-	410.6	631.9	486.6	544.4	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C8-532AXSP06	382.50	599.4	457.7	514.8	-	383.4	595.2	456.3	511.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C8-625AXSP06	442.90	681.1	525	587.5	-	444.3	675.4	522.3	583.3	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C8-632AXSP06	418.10	649	498.3	559.1	-	419.3	643.7	495.9	555.1	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C9-425AXSP04	335.90	552.2	415.5	471.6	944.1	343.2	551.8	417.4	472.2	932.8	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C9-432AXSP04	307.10	511.5	382.7	436.5	879.8	314.8	511.9	385.3	437	871	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550C9-525AXSP06	409.80	636.9	488.1	548	-	410.6	631.9	486.6	544.4	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C9-532AXSP06	382.50	599.4	457.7	514.8	-	383.4	595.2	456.3	511.9	-	507	31.4	3"	406	20.7	3"	609	39.4	4"
EAW-VD155SZK550C9-625AXSP06	442.90	681.1	525	587.5	-	444.3	675.4	522.3	583.3	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550C9-632AXSP06	418.10	649	498.3	559.1	-	419.3	643.7	495.9	555.1	-	609	28.8	4"	487	22.1	3"	730	40.4	4"
EAW-VD155SZK550K2-425AXSP04	322.20	529.9	398.8	452.3	904.3	329.7	529.7	401.4	453	895.2	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550K2-432AXSP04	295.50	492.5	368.6	420.8	847	303.3	493.3	371.2	421.5	839.1	609	19.9	4"	487	16.2	3"	730	28	4"
EAW-VD155SZK550K2-525AXSP06	391.60	608.3	466.8	523.8	-	393.1	603.8	465	519.9	-	507	31.4	3"	406	20.7	3"			



EAW-VD1556PB370C8-532AXSP04	316.30	515.4	388.6	440.7	876.2	322.8	515.3	390.9	441.3	868.9	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370C8-625AXSP04	361.00	577.2	439.4	495.6	963.1	368.6	577	442.2	496.8	954.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370C8-632AXSP04	342.30	554.3	419.6	474.9	934.3	349.7	554.9	422.5	476.2	924.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K2-425AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K2-432AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K2-525AXSP04	325.10	523.5	396.6	448.4	881.8	331.6	523.4	399.4	449	874	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K2-532AXSP04	304.50	495.8	374.3	424.2	842.6	311.1	496.1	377	425.3	835.3	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K2-625AXSP04	347.00	554.7	422.1	476.6	924.7	353.8	554.6	424.9	477.2	915.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K2-632AXSP04	328.60	532.7	403.1	456.8	896.7	336	533	405.7	457.8	887.3	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K4-425AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K4-432AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K4-525AXSP04	325.10	523.5	396.6	448.4	881.8	331.6	523.4	399.4	449	874	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K4-532AXSP04	304.50	495.8	374.3	424.2	842.6	311.1	496.1	377	425.3	835.3	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K4-625AXSP04	347.00	554.7	422.1	476.6	924.7	353.8	554.6	424.9	477.2	915.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K4-632AXSP04	328.60	532.7	403.1	456.8	896.7	336	533	405.7	457.8	887.3	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K5-425AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K5-432AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K5-525AXSP04	325.10	523.5	396.6	448.4	881.8	331.6	523.4	399.4	449	874	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K5-532AXSP04	304.50	495.8	374.3	424.2	842.6	311.1	496.1	377	425.3	835.3	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K5-625AXSP04	347.00	554.7	422.1	476.6	924.7	353.8	554.6	424.9	477.2	915.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K5-632AXSP04	328.60	532.7	403.1	456.8	896.7	336	533	405.7	457.8	887.3	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K8-425AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K8-432AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB370K8-525AXSP04	325.10	523.5	396.6	448.4	881.8	331.6	523.4	399.4	449	874	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K8-532AXSP04	304.50	495.8	374.3	424.2	842.6	311.1	496.1	377	425.3	835.3	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB370K8-625AXSP04	347.00	554.7	422.1	476.6	924.7	353.8	554.6	424.9	477.2	915.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB370K8-632AXSP04	328.60	532.7	403.1	456.8	896.7	336	533	405.7	457.8	887.3	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400B3-425AXSP04	297.30	481.4	362.6	411.3	-	302.8	481.7	365.3	412.3	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400B3-432AXSP04	274.30	448.8	337.1	383	-	279.8	449.9	339.9	384.6	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400B3-525AXSP04	327.40	526.5	399.4	451.6	888.2	334.3	527	402.1	452.7	880.2	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400B3-532AXSP04	307.20	500.5	377.8	428.2	850.9	314	501.1	380	428.7	842.7	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400B3-625AXSP04	347.40	556.2	423.3	477.9	926.1	355.5	556.5	426.3	478.8	918.5	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400B3-632AXSP04	330.80	536.3	405.8	459.9	901.9	338.7	536.5	408.9	460.7	894.6	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400C3-425AXSP04	305.50	495.7	372.9	423.1	-	311.2	496	375.6	424.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400C3-432AXSP04	281.50	461.1	345.9	393.1	-	287.1	461.9	348	393.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400C3-525AXSP04	338.90	544.3	412.4	466.5	919.3	345.3	545.1	414.8	467.3	910.2	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400C3-532AXSP04	316.30	515.4	388.6	440.7	876.2	322.8	515.3	390.9	441.3	868.9	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400C3-625AXSP04	361.00	577.2	439.4	495.6	963.1	368.6	577	442.2	496.8	954.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400C3-632AXSP04	342.30	554.3	419.6	474.9	934.3	349.7	554.9	422.5	476.2	924.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400C9-425AXSP04	305.50	495.7	372.9	423.1	-	311.2	496	375.6	424.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400C9-432AXSP04	281.50	461.1	345.9	393.1	-	287.1	461.9	348	393.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400C9-525AXSP04	338.90	544.3	412.4	466.5	919.3	345.3	545.1	414.8	467.3	910.2	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400C9-532AXSP04	316.30	515.4	388.6	440.7	876.2	322.8	515.3	390.9	441.3	868.9	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400C9-625AXSP04	361.00	577.2	439.4	495.6	963.1	368.6	577	442.2	496.8	954.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400C9-632AXSP04	342.30	554.3	419.6	474.9	934.3	349.7	554.9	422.5	476.2	924.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400K3-425AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400K3-432AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400K3-525AXSP04	325.10	523.5	396.6	448.4	881.8	331.6	523.4	399.4	449	874	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400K3-532AXSP04	304.50	495.8	374.3	424.2	842.6	311.1	496.1	377	425.3	835.3	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400K3-625AXSP04	347.00	554.7	422.1	476.6	924.7	353.8	554.6	424.9	477.2	915.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400K3-632AXSP04	328.60	532.7	403.1	456.8	896.7	336	533	405.7	457.8	887.3	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400K9-425AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400K9-432AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400K9-525AXSP04	325.10	523.5	396.6	448.4	881.8	331.6	523.4	399.4	449	874	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400K9-532AXSP04	304.50	495.8	374.3	424.2	842.6	311.1	496.1	377	425.3	835.3	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400K3-625AXSP04	347.00	554.7	422.1	476.6	924.7	353.8	554.6	424.9	477.2	915.2	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400K3-632AXSP04	328.60	532.7	403.1	456.8	896.7	336	533	405.7	457.8	887.3	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB400K9-625AXSP04	294.60	476.7	359.2	407.3	-	299.8	477.5	361.6	408.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400K9-632AXSP04	271.20	444.3	333.6	379.2	-	276.7	444.9	335.7	379.8	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400R3-425AXSP04	299.30	484.9	365.1	414.2	-	304.8	485.3	367.8	415.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400R3-432AXSP04	276.10	452.4	339.4	385.9	-	281.6	453.3	341.7	386.7	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB400R3-525AXSP04	330.60	532.1	403.5	455.6	896.7	337.4	532.2	405.9	457	889.1	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB400R3-532AXSP04	309.20	504.1	380.4	431.2	857.4	316.2	504.8	383.3	431.8	849.1	564	20.9	4"	451	16.3	3"	676		

EAW-VD1556PB550C9-525AXSP04	380.80	611.9	462.2	523.9	-	387.6	612.9	465.8	524.8	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550C9-532AXSP04	354.20	575.8	434	492.4	-	361.7	577.4	436.6	493.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550C9-625AXSP04	408.20	650.8	494.9	559.1	1090.9	416.2	652	498.6	560.3	1082.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K2-632AXSP04	385.20	622.1	471	533.3	1052.9	393.3	623	474.5	534.1	1043.6	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K2-425AXSP04	325.60	528.8	397.9	451.3	-	331.5	529.9	400.8	453.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K2-432AXSP04	300.80	491.5	368.4	419.2	-	306.5	493.2	371.4	420.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K2-525AXSP04	362.40	581.5	440.1	498.4	-	369.3	582.4	443.4	499.2	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K2-532AXSP04	338.00	549.5	414.4	469.7	936.7	345	551	417.5	471.1	930	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K2-625AXSP04	386.80	617.8	470.6	530.5	1034.1	394.6	618.7	473.2	532.1	1024.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K2-632AXSP04	365.60	591.6	448.8	507	999.5	374.2	593	451.8	508.2	990.4	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K3-425AXSP04	325.60	528.8	397.9	451.3	-	331.5	529.9	400.8	453.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K3-432AXSP04	300.80	491.5	368.4	419.2	-	306.5	493.2	371.4	420.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K3-525AXSP04	362.40	581.5	440.1	498.4	-	369.3	582.4	443.4	499.2	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K3-532AXSP04	338.00	549.5	414.4	469.7	936.7	345	551	417.5	471.1	930	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K3-625AXSP04	386.80	617.8	470.6	530.5	1034.1	394.6	618.7	473.2	532.1	1024.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K3-632AXSP04	365.60	591.6	448.8	507	999.5	374.2	593	451.8	508.2	990.4	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K4-425AXSP04	325.60	528.8	397.9	451.3	-	331.5	529.9	400.8	453.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K4-432AXSP04	300.80	491.5	368.4	419.2	-	306.5	493.2	371.4	420.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K4-525AXSP04	362.40	581.5	440.1	498.4	-	369.3	582.4	443.4	499.2	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K4-532AXSP04	338.00	549.5	414.4	469.7	936.7	345	551	417.5	471.1	930	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K4-625AXSP04	386.80	617.8	470.6	530.5	1034.1	394.6	618.7	473.2	532.1	1024.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K4-632AXSP04	365.60	591.6	448.8	507	999.5	374.2	593	451.8	508.2	990.4	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K5-425AXSP04	325.60	528.8	397.9	451.3	-	331.5	529.9	400.8	453.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K5-432AXSP04	300.80	491.5	368.4	419.2	-	306.5	493.2	371.4	420.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K5-432AXSP04	362.40	581.5	440.1	498.4	-	369.3	582.4	443.4	499.2	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K5-532AXSP04	338.00	549.5	414.4	469.7	936.7	345	551	417.5	471.1	930	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K5-625AXSP04	386.80	617.8	470.6	530.5	1034.1	394.6	618.7	473.2	532.1	1024.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K5-632AXSP04	365.60	591.6	448.8	507	999.5	374.2	593	451.8	508.2	990.4	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K8-425AXSP04	325.60	528.8	397.9	451.3	-	331.5	529.9	400.8	453.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K8-432AXSP04	300.80	491.5	368.4	419.2	-	306.5	493.2	371.4	420.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K8-525AXSP04	362.40	581.5	440.1	498.4	-	369.3	582.4	443.4	499.2	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K8-532AXSP04	338.00	549.5	414.4	469.7	936.7	345	551	417.5	471.1	930	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K9-425AXSP04	325.60	528.8	397.9	451.3	-	331.5	529.9	400.8	453.1	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K9-432AXSP04	300.80	491.5	368.4	419.2	-	306.5	493.2	371.4	420.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550K9-525AXSP04	362.40	581.5	440.1	498.4	-	369.3	582.4	443.4	499.2	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K9-532AXSP04	338.00	549.5	414.4	469.7	936.7	345	551	417.5	471.1	930	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550K9-625AXSP04	386.80	617.8	470.6	530.5	1034.1	394.6	618.7	473.2	532.1	1024.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550K9-632AXSP04	365.60	591.6	448.8	507	999.5	374.2	593	451.8	508.2	990.4	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550R3-425AXSP04	333.20	541.7	407.1	462	-	339.2	543.2	410.3	464.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550R3-432AXSP04	307.90	503.6	377.4	429.2	-	313.6	504.7	380.3	430.9	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB550R3-525AXSP04	371.30	595.6	451.1	510.2	-	378	596.8	454	512.1	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550R3-532AXSP04	346.20	562.7	423.9	480.7	-	353.6	563.6	427.4	482.4	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB550R3-625AXSP04	396.70	633.3	482.1	543.7	1060.8	404.4	633.7	485	544.8	1051.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB550R3-632AXSP04	375.00	606.6	459.1	519.6	1024.2	382.8	607.5	462.4	521.1	1016.6	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C2-425AXSP04	360.20	586.6	440.4	500	-	366.9	588.1	444	502.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C2-432AXSP04	331.70	543.9	407.1	463.5	-	338.2	545.2	410.6	465.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C2-525AXSP04	401.50	646.4	487.9	552.6	-	409	648	492	554.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750C2-532AXSP04	375.70	609	458.5	520.9	-	383.2	610.9	462.2	522.5	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750C2-625AXSP04	430.50	685.9	521.5	588.7	-	439.4	688	525.2	590.5	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C2-632AXSP04	406.90	657.2	496.5	562.7	1113	415.7	658.4	501.2	564.6	1105	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C3-425AXSP04	360.20	586.6	440.4	500	-	366.9	588.1	444	502.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C3-432AXSP04	331.70	543.9	407.1	463.5	-	338.2	545.2	410.6	465.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C3-525AXSP04	401.50	646.4	487.9	552.6	-	409	648	492	554.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750C3-532AXSP04	375.70	609	458.5	520.9	-	383.2	610.9	462.2	522.5	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750C3-625AXSP04	430.50	685.9	521.5	588.7	-	439.4	688	525.2	590.5	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C3-632AXSP04	406.90	657.2	496.5	562.7	1113	415.7	658.4	501.2	564.6	1105	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C4-425AXSP04	360.20	586.6	440.4	500	-	366.9	588.1	444	502.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C4-432AXSP04	331.70	543.9	407.1	463.5	-	338.2	545.2	410.6	465.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C4-525AXSP04	401.50	646.4	487.9	552.6	-	409	648	492	554.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750C4-532AXSP04	375.70	609	458.5	520.9	-	383.2	610.9	462.2	522.5	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750C4-625AXSP04	430.50	685.9	521.5	588.7	-	439.4	688	525.2	590.5	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C4-632AXSP04	406.90	657.2	496.5	562.7	1113	415.7	658.4	501.2	564.6	1105	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750C5-425AXSP04	360.20	586.6	440.4	500	-	366.9	588.1	444	502.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750C5-432AXSP04	331.70	543.9	407.1	463.5	-	338.2	545.2	410.6	465.2	-	451	22.7	3"	361	15	3"	541	28.3	4

EAW-VD1556PB750K5-432AXSP04	321.70	526.8	394.5	449.1	-	328	528.9	397.9	450.9	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K5-525AXSP04	388.00	624.3	471.9	534.2	-	395.6	625.3	475.5	535.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K5-532AXSP04	362.90	588.6	443.2	503.1	-	370.5	590.3	446.6	505.4	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K5-625AXSP04	415.10	662.4	503.4	568.9	1111	424.2	664.1	507.5	570.4	1103.5	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K5-632AXSP04	392.90	634.3	479.8	543.5	1074.3	401.6	635.8	483.9	544.9	1065.9	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K8-425AXSP04	348.20	567.2	426	484	-	355.2	568.4	429.1	485.9	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K8-432AXSP04	321.70	526.8	394.5	449.1	-	328	528.9	397.9	450.9	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K8-532AXSP04	388.00	624.3	471.9	534.2	-	395.6	625.3	475.5	535.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K8-532AXSP04	362.90	588.6	443.2	503.1	-	370.5	590.3	446.6	505.4	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K8-625AXSP04	415.10	662.4	503.4	568.9	1111	424.2	664.1	507.5	570.4	1103.5	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K8-632AXSP04	392.90	634.3	479.8	543.5	1074.3	401.6	635.8	483.9	544.9	1065.9	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K9-425AXSP04	348.20	567.2	426	484	-	355.2	568.4	429.1	485.9	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K9-432AXSP04	321.70	526.8	394.5	449.1	-	328	528.9	397.9	450.9	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K9-525AXSP04	388.00	624.3	471.9	534.2	-	395.6	625.3	475.5	535.9	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K9-532AXSP04	362.90	588.6	443.2	503.1	-	370.5	590.3	446.6	505.4	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K9-625AXSP04	415.10	662.4	503.4	568.9	1111	424.2	664.1	507.5	570.4	1103.5	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K9-632AXSP04	392.90	634.3	479.8	543.5	1074.3	401.6	635.8	483.9	544.9	1065.9	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K9-632AXSP04	341.30	554.5	416.9	473.4	-	347.7	556.5	420.6	475.2	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K9-432AXSP04	315.20	516.7	386.6	440	-	321.6	517.6	389.8	442	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD1556PB750K9-525AXSP04	379.40	610.5	461.2	521.9	-	386.6	611.3	464.6	524.3	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K9-532AXSP04	354.60	576.4	433.7	492.1	-	362.6	577.9	437.7	494.3	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD1556PB750K9-625AXSP04	405.40	646.9	492.1	555.1	1084.3	414	648.4	495.9	557.2	1076.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PB750K9-632AXSP04	383.60	620.5	469.8	531.1	1048.6	392	621.9	473	533.2	1041.6	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD1556PK370C2-425AXSP04	328.30	526.6	398.3	450.5	-	332.7	525.8	399.5	450.6	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C2-432AXSP04	303.70	489.9	369.2	418.7	-	307.6	490	370.5	418.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C2-525AXSP04	366.10	580.4	441.1	497.6	-	371	578.8	442.3	496.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C2-532AXSP04	342.00	548.2	415.4	469.6	926.3	346.7	546.9	416.9	469.2	916.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C2-625AXSP04	391.50	616.1	471.5	529.8	1021.1	396.7	614.6	472.7	529.2	1008.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C2-632AXSP04	370.60	590.5	450.4	507.6	987.8	376.5	589.4	451.3	506.6	976.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C4-425AXSP04	328.30	526.6	398.3	450.5	-	332.7	525.8	399.5	450.6	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C4-432AXSP04	303.70	489.9	369.2	418.7	-	307.6	490	370.5	418.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C4-525AXSP04	366.10	580.4	441.1	497.6	-	371	578.8	442.3	496.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C4-532AXSP04	342.00	548.2	415.4	469.6	926.3	346.7	546.9	416.9	469.2	916.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C4-625AXSP04	391.50	616.1	471.5	529.8	1021.1	396.7	614.6	472.7	529.2	1008.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C4-632AXSP04	370.60	590.5	450.4	507.6	987.8	376.5	589.4	451.3	506.6	976.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C5-425AXSP04	328.30	526.6	398.3	450.5	-	332.7	525.8	399.5	450.6	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C5-432AXSP04	303.70	489.9	369.2	418.7	-	307.6	490	370.5	418.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C5-525AXSP04	366.10	580.4	441.1	497.6	-	371	578.8	442.3	496.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C5-532AXSP04	342.00	548.2	415.4	469.6	926.3	346.7	546.9	416.9	469.2	916.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C5-625AXSP04	391.50	616.1	471.5	529.8	1021.1	396.7	614.6	472.7	529.2	1008.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C5-632AXSP04	370.60	590.5	450.4	507.6	987.8	376.5	589.4	451.3	506.6	976.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C8-425AXSP04	328.30	526.6	398.3	450.5	-	332.7	525.8	399.5	450.6	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C8-432AXSP04	303.70	489.9	369.2	418.7	-	307.6	490	370.5	418.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370C8-525AXSP04	366.10	580.4	441.1	497.6	-	371	578.8	442.3	496.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C8-532AXSP04	342.00	548.2	415.4	469.6	926.3	346.7	546.9	416.9	469.2	916.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370C8-625AXSP04	391.50	616.1	471.5	529.8	1021.1	396.7	614.6	472.7	529.2	1008.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370C8-632AXSP04	370.60	590.5	450.4	507.6	987.8	376.5	589.4	451.3	506.6	976.7	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370K2-425AXSP04	316.30	507	383.5	434.1	-	320.4	506.1	384.5	433.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370K2-432AXSP04	292.50	472.8	356.4	403.8	-	296.5	471.9	357.4	403.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370K2-525AXSP04	351.50	557	423.9	477.9	932.1	355.9	556	425.4	477.7	921.6	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370K2-532AXSP04	328.90	527.6	399.8	451.7	890.2	333.8	526.2	401.1	451.2	879.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370K2-625AXSP04	375.00	590.9	452.7	508.4	977.2	380.4	589.2	453.6	507.6	966.1	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370K2-632AXSP04	356.00	567.7	432.3	487	947.3	361.4	565.7	433	486.6	936.3	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370K4-425AXSP04	316.30	507	383.5	434.1	-	320.4	506.1	384.5	433.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370K4-432AXSP04	292.50	472.8	356.4	403.8	-	296.5	471.9	357.4	403.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370K4-525AXSP04	351.50	557	423.9	477.9	932.1	355.9	556	425.4	477.7	921.6	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370K4-532AXSP04	328.90	527.6	399.8	451.7	890.2	333.8	526.2	401.1	451.2	879.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370K4-625AXSP04	375.00	590.9	452.7	508.4	977.2	380.4	589.2	453.6	507.6	966.1	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370K4-632AXSP04	356.00	567.7	432.3	487	947.3	361.4	565.7	433	486.6	936.3	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK370K5-425AXSP04	316.30	507	383.5	434.1	-	320.4	506.1	384.5	433.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370K5-432AXSP04	292.50	472.8	356.4	403.8	-	296.5	471.9	357.4	403.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK370K5-525AXSP04	351.50	557	423.9	477.9	932.1	355.9	556	425.4	477.7	921.6	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370K5-532AXSP04	328.90	527.6	399.8	451.7	890.2	333.8	526.2	401.1	451.2	879.9	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK370K5-625AXSP04																			

EAW-VD1556PK400R3-425AXSP04	322.10	516	390.7	441.6	-	326.5	515.4	391.9	441.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK400R3-432AXSP04	298.20	481.4	363.2	411.6	-	302.4	480.7	364.4	411	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK400R3-432AXSP04	357.50	566.9	431.9	486.3	-	362.7	565.4	433	486.3	939	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK400R3-532AXSP04	334.80	536.9	407.2	460.1	906.5	340	535.7	408.7	459.8	897.6	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK400R3-625AXSP04	381.60	600.9	460.2	516.9	995.3	387.3	599.4	461.3	516.3	983.3	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK400R3-632AXSP04	362.00	577.8	439.7	496.2	964.6	367.7	576	441.3	495.3	955	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500R3-425AXSP04	349.40	562.1	424.6	480.8	-	354.3	561.3	426	480.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500R3-432AXSP04	323.20	523.2	393.5	446.2	-	327.8	523.2	395	447.1	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500R3-525AXSP04	389.10	617.9	469.2	529.8	-	394.4	617.1	471.3	529.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500R3-532AXSP04	364.90	584.1	442.1	500.4	-	370.1	584	444	500.3	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500R3-625AXSP04	415.90	654.3	499.9	562.8	1085.9	421.9	653.3	502.3	562.7	1076.1	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500R3-632AXSP04	394.80	629	478.7	539.2	1054	401.1	627.9	479.8	539.1	1043.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C2-425AXSP04	366.80	589.9	445.4	504.8	-	371.9	589.9	446.7	504.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C2-432AXSP04	337.60	546.9	411.5	466.9	-	342	546.8	413.2	467.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C2-525AXSP04	410.60	653.2	495.7	560.2	-	416.1	652.1	497.7	560.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C2-532AXSP04	383.00	614.2	464.6	526.3	-	388.3	613.5	466.3	525.8	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C2-625AXSP04	443.20	697	532.3	598.9	-	448.6	695.3	533.6	598.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C2-632AXSP04	417.90	664.7	505.6	569.9	1117.4	423.8	663.3	507.3	569.6	1105.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C3-425AXSP04	366.80	589.9	445.4	504.8	-	371.9	589.9	446.7	504.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C3-432AXSP04	337.60	546.9	411.5	466.9	-	342	546.8	413.2	467.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C3-525AXSP04	410.60	653.2	495.7	560.2	-	416.1	652.1	497.7	560.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C3-532AXSP04	383.00	614.2	464.6	526.3	-	388.3	613.5	466.3	525.8	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C3-625AXSP04	443.20	697	532.3	598.9	-	448.6	695.3	533.6	598.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C3-632AXSP04	417.90	664.7	505.6	569.9	1117.4	423.8	663.3	507.3	569.6	1105.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C4-425AXSP04	366.80	589.9	445.4	504.8	-	371.9	589.9	446.7	504.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C4-432AXSP04	337.60	546.9	411.5	466.9	-	342	546.8	413.2	467.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C4-525AXSP04	410.60	653.2	495.7	560.2	-	416.1	652.1	497.7	560.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C4-532AXSP04	383.00	614.2	464.6	526.3	-	388.3	613.5	466.3	525.8	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C4-625AXSP04	443.20	697	532.3	598.9	-	448.6	695.3	533.6	598.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C4-632AXSP04	417.90	664.7	505.6	569.9	1117.4	423.8	663.3	507.3	569.6	1105.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C5-425AXSP04	366.80	589.9	445.4	504.8	-	371.9	589.9	446.7	504.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C5-432AXSP04	337.60	546.9	411.5	466.9	-	342	546.8	413.2	467.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C5-525AXSP04	410.60	653.2	495.7	560.2	-	416.1	652.1	497.7	560.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C5-532AXSP04	383.00	614.2	464.6	526.3	-	388.3	613.5	466.3	525.8	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C5-625AXSP04	443.20	697	532.3	598.9	-	448.6	695.3	533.6	598.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C5-632AXSP04	417.90	664.7	505.6	569.9	1117.4	423.8	663.3	507.3	569.6	1105.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C8-425AXSP04	366.80	589.9	445.4	504.8	-	371.9	589.9	446.7	504.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C8-432AXSP04	337.60	546.9	411.5	466.9	-	342	546.8	413.2	467.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C8-525AXSP04	410.60	653.2	495.7	560.2	-	416.1	652.1	497.7	560.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C8-532AXSP04	383.00	614.2	464.6	526.3	-	388.3	613.5	466.3	525.8	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C8-625AXSP04	443.20	697	532.3	598.9	-	448.6	695.3	533.6	598.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C8-632AXSP04	417.90	664.7	505.6	569.9	1117.4	423.8	663.3	507.3	569.6	1105.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C9-425AXSP04	366.80	589.9	445.4	504.8	-	371.9	589.9	446.7	504.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C9-432AXSP04	337.60	546.9	411.5	466.9	-	342	546.8	413.2	467.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500C9-525AXSP04	410.60	653.2	495.7	560.2	-	416.1	652.1	497.7	560.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C9-532AXSP04	383.00	614.2	464.6	526.3	-	388.3	613.5	466.3	525.8	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500C9-625AXSP04	443.20	697	532.3	598.9	-	448.6	695.3	533.6	598.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500C9-632AXSP04	417.90	664.7	505.6	569.9	1117.4	423.8	663.3	507.3	569.6	1105.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500K2-425AXSP04	351.40	564.4	426.3	482.7	-	355.5	563.4	427.5	482.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500K2-432AXSP04	323.90	524.4	394.8	448.1	-	328.7	524.4	396.6	448	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500K2-525AXSP04	391.80	621.5	472.6	532.8	-	397	620.5	473.7	532.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500K2-532AXSP04	366.60	587.1	444.3	502.9	-	371.6	586.5	445.9	502.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500K2-625AXSP04	420.00	660.9	504.8	567.7	1097.2	425.6	659.2	506.7	567.7	1086.1	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500K2-632AXSP04	397.50	632.7	481.4	543.1	1060.5	403.2	631.4	483	542.7	1049.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500K3-425AXSP04	351.40	564.4	426.3	482.7	-	355.5	563.4	427.5	482.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500K3-432AXSP04	323.90	524.4	394.8	448.1	-	328.7	524.4	396.6	448	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500K3-525AXSP04	391.80	621.5	472.6	532.8	-	397	620.5	473.7	532.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500K3-532AXSP04	366.60	587.1	444.3	502.9	-	371.6	586.5	445.9	502.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500K3-625AXSP04	420.00	660.9	504.8	567.7	1097.2	425.6	659.2	506.7	567.7	1086.1	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500K3-632AXSP04	397.50	632.7	481.4	543.1	1060.5	403.2	631.4	483	542.7	1049.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556PK500K4-425AXSP04	351.40	564.4	426.3	482.7	-	355.5	563.4	427.5	482.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500K4-432AXSP04	323.90	524.4	394.8	448.1	-	328.7	524.4	396.6	448	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD1556PK500K4-525AXSP04	391.80	621.5	472.6	532.8	-	397	620.5	473.7	532.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD1556PK500K4-532AXSP04	366.60	587.1	444.3	502.9	-	371.6	586.5	445.9	502.4	-	564	22.9	4"	451					

EAW-VD1556PK750C3-632AXSP04	443.40	705.5	536.2	605	-	450	705.3	538.3	605.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750C4-425AXSP02	-	554.8	390.5	462	1002.4	-	313.1	567.5	408.8	475.6	1003.2	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD1556PK750C4-432AXSP04	359.00	582.8	437.5	497.1	-	364.1	582.8	439.7	497.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750C4-525AXSP04	435.50	694.1	526.4	594.5	-	441.6	694.3	528.7	595.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750C4-532AXSP04	406.90	653.1	493.5	558.7	-	412.8	653.7	496.3	559.3	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750C4-625AXSP04	468.70	738.2	563.5	634.5	-	475.6	737.9	565.3	635.1	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750C4-632AXSP04	443.40	705.5	536.2	605	-	450	705.3	538.3	605.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750C5-425AXSP02	-	554.8	390.5	462	1002.4	-	313.1	567.5	408.8	475.6	1003.2	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD1556PK750C5-432AXSP04	359.00	582.8	437.5	497.1	-	364.1	582.8	439.7	497.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750C5-525AXSP04	435.50	694.1	526.4	594.5	-	441.6	694.3	528.7	595.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750C5-532AXSP04	406.90	653.1	493.5	558.7	-	412.8	653.7	496.3	559.3	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750C5-625AXSP04	468.70	738.2	563.5	634.5	-	475.6	737.9	565.3	635.1	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750C5-632AXSP04	443.40	705.5	536.2	605	-	450	705.3	538.3	605.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750C8-425AXSP02	-	554.8	390.5	462	1002.4	-	313.1	567.5	408.8	475.6	1003.2	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD1556PK750C8-432AXSP04	359.00	582.8	437.5	497.1	-	364.1	582.8	439.7	497.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750C8-525AXSP04	435.50	694.1	526.4	594.5	-	441.6	694.3	528.7	595.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750C8-532AXSP04	406.90	653.1	493.5	558.7	-	412.8	653.7	496.3	559.3	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750C8-625AXSP04	468.70	738.2	563.5	634.5	-	475.6	737.9	565.3	635.1	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750C8-632AXSP04	443.40	705.5	536.2	605	-	450	705.3	538.3	605.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K2-425AXSP04	377.30	607.8	458.3	519.7	-	382.4	608	460.5	519.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K2-432AXSP04	348.00	564	424.1	481.5	-	352.7	563.7	426.1	482.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K2-525AXSP04	420.20	669.3	507.5	573.7	-	426.6	669.3	510.4	573.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K2-532AXSP04	393.60	631.3	477.8	540.6	-	399.3	632	479.7	541.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K2-625AXSP04	452.10	711.8	543.2	611.3	-	458.3	710.9	545.3	611.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K2-632AXSP04	428.00	680.6	517.2	584.1	-	434.1	680.2	519.8	583.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K3-425AXSP04	377.30	607.8	458.3	519.7	-	382.4	608	460.5	519.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K3-432AXSP04	348.00	564	424.1	481.5	-	352.7	563.7	426.1	482.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K3-525AXSP04	420.20	669.3	507.5	573.7	-	426.6	669.3	510.4	573.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K3-532AXSP04	393.60	631.3	477.8	540.6	-	399.3	632	479.7	541.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K3-625AXSP04	452.10	711.8	543.2	611.3	-	458.3	710.9	545.3	611.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K3-632AXSP04	428.00	680.6	517.2	584.1	-	434.1	680.2	519.8	583.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K4-425AXSP04	377.30	607.8	458.3	519.7	-	382.4	608	460.5	519.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K4-432AXSP04	348.00	564	424.1	481.5	-	352.7	563.7	426.1	482.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K4-525AXSP04	420.20	669.3	507.5	573.7	-	426.6	669.3	510.4	573.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K4-532AXSP04	393.60	631.3	477.8	540.6	-	399.3	632	479.7	541.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K4-625AXSP04	452.10	711.8	543.2	611.3	-	458.3	710.9	545.3	611.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K4-632AXSP04	428.00	680.6	517.2	584.1	-	434.1	680.2	519.8	583.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K5-425AXSP04	377.30	607.8	458.3	519.7	-	382.4	608	460.5	519.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K5-432AXSP04	348.00	564	424.1	481.5	-	352.7	563.7	426.1	482.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K5-525AXSP04	420.20	669.3	507.5	573.7	-	426.6	669.3	510.4	573.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K5-532AXSP04	393.60	631.3	477.8	540.6	-	399.3	632	479.7	541.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K5-625AXSP04	452.10	711.8	543.2	611.3	-	458.3	710.9	545.3	611.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K5-632AXSP04	428.00	680.6	517.2	584.1	-	434.1	680.2	519.8	583.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K8-425AXSP04	377.30	607.8	458.3	519.7	-	382.4	608	460.5	519.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K8-432AXSP04	348.00	564	424.1	481.5	-	352.7	563.7	426.1	482.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K8-525AXSP04	420.20	669.3	507.5	573.7	-	426.6	669.3	510.4	573.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K8-532AXSP04	393.60	631.3	477.8	540.6	-	399.3	632	479.7	541.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K8-625AXSP04	452.10	711.8	543.2	611.3	-	458.3	710.9	545.3	611.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K8-632AXSP04	428.00	680.6	517.2	584.1	-	434.1	680.2	519.8	583.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K9-425AXSP04	377.30	607.8	458.3	519.7	-	382.4	608	460.5	519.8	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K9-432AXSP04	348.00	564	424.1	481.5	-	352.7	563.7	426.1	482.4	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750K9-525AXSP04	420.20	669.3	507.5	573.7	-	426.6	669.3	510.4	573.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K9-532AXSP04	393.60	631.3	477.8	540.6	-	399.3	632	479.7	541.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750K9-625AXSP04	452.10	711.8	543.2	611.3	-	458.3	710.9	545.3	611.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750K9-632AXSP04	428.00	680.6	517.2	584.1	-	434.1	680.2	519.8	583.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750R3-425AXSP04	369.30	594	448.3	508.2	-	375	594.2	450.6	509.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750R3-432AXSP04	341.00	552.3	415.8	471.8	-	345.9	553	417.6	472.6	-	451	24.7	3"	361	16.3	3"	541	31.1	4"	
EAW-VD1556PK750R3-525AXSP04	411.40	654.4	496.6	560.4	-	416.8	653.3	498.6	561.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750R3-532AXSP04	385.20	618	467.4	528.6	-	390.7	617.5	469.2	529.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"	
EAW-VD1556PK750R3-625AXSP04	441.50	694.3	530.3	596.6	-	448.1	694.3	532.2	597.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"	
EAW-VD1556PK750R3-632AXSP04	417.70	665.6	505.5	570.7	1117.4	-	424.3	665.1	507.9	571.1	1107.2	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD1556ZB370C2-425AXSP04	350.20	569	429	486.1	965.6	-	356.6	567.5	430.6	485.8	955.3	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB370C2-432AXSP04	321.50	529	397.4	451.5	905.3	328.2	528.5	399.1	452	895.1	609	21.3	4"	487	17.1	3"	730	29.9	4"	
EAW-VD1556ZB370C2-525AXSP04	387.40	625.1	473.9	535.8	1049.2	-	394.7	623.4	475.4	535.2	1036.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB370C2-532AXSP06	394.20	615.4	470.5	528.6	-	394.9	610.1	468.1	524.7	-	507	33.4	3"	406	22	3"	609	42.2		

Note: "-" indicates flow rate is outside of unit capability

EAW-VD1556ZB370K4-625AXSP06	434.30	661.7	512.3	571.8	-	434.3	655.5	509.5	567	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB370K4-632AXSP06	412.60	635.7	489.7	548	-	413.1	629.8	486.7	543.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB370K5-425AXSP04	336.50	547.4	413.3	468.1	928.8	343.2	546	414.9	467.8	917.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB370K5-432AXSP04	310.10	510.7	383.7	435.6	872.6	316.5	509.5	385.3	436.1	862.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB370K5-525AXSP06	404.30	624.3	480.2	537.6	-	405	618.7	477.4	533.4	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB370K5-532AXSP06	379.50	591.3	452.7	508.3	-	380.8	586.4	450.5	504.7	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB370K5-625AXSP06	434.30	661.7	512.3	571.8	-	434.3	655.5	509.5	567	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB370K5-632AXSP06	412.60	635.7	489.7	548	-	413.1	629.8	486.7	543.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB370K8-425AXSP04	336.50	547.4	413.3	468.1	928.8	343.2	546	414.9	467.8	917.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB370K8-432AXSP04	310.10	510.7	383.7	435.6	872.6	316.5	509.5	385.3	436.1	862.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB370K8-525AXSP06	404.30	624.3	480.2	537.6	-	405	618.7	477.4	533.4	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB370K8-532AXSP06	379.50	591.3	452.7	508.3	-	380.8	586.4	450.5	504.7	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB370K8-625AXSP06	434.30	661.7	512.3	571.8	-	434.3	655.5	509.5	567	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB370K8-632AXSP06	412.60	635.7	489.7	548	-	413.1	629.8	486.7	543.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400B3-425AXSP04	341.60	555	418.9	474.5	942.2	347.8	553.8	420.6	474.3	931.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400B3-432AXSP04	314.40	517	388.8	441.6	884	320.7	516.7	390.6	442.2	874.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400B3-525AXSP06	409.70	632.9	486.6	544.9	-	410.6	627.5	484	540.8	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400B3-532AXSP04	351.40	574.8	432.9	491.9	971.9	359.4	573.9	435	492	961.6	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB400B3-625AXSP06	439.00	669.9	518.5	578.9	-	440	664.1	515.5	574.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400B3-632AXSP06	418.10	644.5	496.3	555.4	-	418.7	638.7	493.3	551	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400C3-425AXSP04	350.20	569	429	486.1	965.6	356.6	567.5	430.6	485.8	955.3	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400C3-432AXSP04	321.50	529	397.4	451.5	905.3	328.2	528.5	399.1	452	895.1	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400C3-525AXSP06	387.40	625.1	473.9	535.8	1049.2	394.7	623.4	475.4	535.2	1036.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB400C3-532AXSP06	394.20	615.4	470.5	528.6	-	394.9	610.1	468.1	524.7	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400C3-625AXSP06	453.00	691	534.4	597.5	-	453.1	685.3	531.6	592.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400C3-632AXSP06	429.50	662.7	510	570.9	-	430.1	656.7	506.9	566.3	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400C9-425AXSP04	350.20	569	429	486.1	965.6	356.6	567.5	430.6	485.8	955.3	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400C9-432AXSP04	321.50	529	397.4	451.5	905.3	328.2	528.5	399.1	452	895.1	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400C9-525AXSP06	387.40	625.1	473.9	535.8	1049.2	394.7	623.4	475.4	535.2	1036.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB400C9-532AXSP06	394.20	615.4	470.5	528.6	-	394.9	610.1	468.1	524.7	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400C9-625AXSP06	453.00	691	534.4	597.5	-	453.1	685.3	531.6	592.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400C9-632AXSP06	429.50	662.7	510	570.9	-	430.1	656.7	506.9	566.3	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400K3-425AXSP04	336.50	547.4	413.3	468.1	928.8	343.2	546	414.9	467.8	917.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400K3-432AXSP04	310.10	510.7	383.7	435.6	872.6	316.5	509.5	385.3	436.1	862.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400K3-525AXSP06	404.30	624.3	480.2	537.6	-	405	618.7	477.4	533.4	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400K3-532AXSP06	379.50	591.3	452.7	508.3	-	380.8	586.4	450.5	504.7	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400K3-625AXSP06	434.30	661.7	512.3	571.8	-	434.3	655.5	509.5	567	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400K3-632AXSP06	412.60	635.7	489.7	548	-	413.1	629.8	486.7	543.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400K9-425AXSP04	336.50	547.4	413.3	468.1	928.8	343.2	546	414.9	467.8	917.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400K9-432AXSP04	310.10	510.7	383.7	435.6	872.6	316.5	509.5	385.3	436.1	862.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400K9-525AXSP06	404.30	624.3	480.2	537.6	-	405	618.7	477.4	533.4	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400K9-532AXSP06	379.50	591.3	452.7	508.3	-	380.8	586.4	450.5	504.7	-	507	33.4	3"	406	22	3"	609	42.2	4"
EAW-VD1556ZB400K9-625AXSP06	434.30	661.7	512.3	571.8	-	434.3	655.5	509.5	567	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400K9-632AXSP06	412.60	635.7	489.7	548	-	413.1	629.8	486.7	543.5	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400R3-425AXSP04	343.60	558.5	421.4	477.4	948.5	350	557.5	423.3	478.1	937.8	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400R3-432AXSP04	316.60	521.3	391.2	445.2	891.5	323.4	520.2	393.8	445.1	881.9	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB400R3-525AXSP06	378.80	611.6	464	525.2	1026	366.6	610.9	465.5	524.7	1013.9	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB400R3-532AXSP04	354.00	579.3	436.2	495.7	979.6	361.3	577.7	438.4	495.1	968.1	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB400R3-625AXSP06	443.00	675.3	522.5	583.4	-	443.2	669.2	519.3	578.7	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB400R3-632AXSP06	421.10	648.4	499.2	559.5	-	421.8	643.5	497	555.1	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550B3-425AXSP04	376.80	610.9	460.7	522.7	-	383.8	610.3	463.3	522.3	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550B3-432AXSP04	346.30	568	426.8	484.7	974.1	353	567.5	429.4	485.2	964.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550B3-525AXSP06	416.60	670.5	508.7	574.8	1129.6	424.6	669.8	511.1	575.1	1117.3	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550B3-532AXSP04	388.10	633.5	477.6	541.8	1075	396.2	632.6	480.7	541.9	1063.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550B3-625AXSP06	484.90	742.2	573.1	640.4	-	486.1	736.7	570.5	636.3	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550B3-632AXSP06	460.30	711.2	547	612.7	-	461.1	706.7	544.5	608.7	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550C2-425AXSP04	394.60	639.3	482	546.4	-	401.1	638.6	483.8	546.8	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550C2-432AXSP04	361.20	592.7	444.6	505.2	-	368	592.1	447.2	505.7	1006.5	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550C2-525AXSP04	438.50	705.6	535.1	605.1	1190.7	446.2	704.6	537.5	605.2	1177.1	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550C2-532AXSP04	406.80	663.8	501.1	567	1126.8	415.2	662.4	503.3	567.8	1115.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550C2-625AXSP04	474.10	758.3	576.9	651.4	1262.9	482.9	756.1	579.1	650.5	1248	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB550C2-632AXSP06	483.50	748.7	574.9	645.3	-	484.9	743.6	572.9	640.8	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550C3-425AXSP04	394.60	639.3	482	546.4	-	401.1	638.6	483.8	546.8	-	609	21.3	4"	487	17.1	3"	730	29.9	4"

EAW-VD1556ZB550K3-532AXSP04	389.40	634.7	479.2	543.6	1077.1	397.5	634.6	481.4	543.6	1065.3	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K3-625AXSP06	487.00	746.6	576.5	644.2	-	487.8	740.4	573.3	639.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K3-632AXSP06	461.80	714.6	548.7	615.6	-	463.1	708.9	546.1	611.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K4-425AXSP04	378.00	611.8	462.1	523.5	-	384.3	612.3	464	524	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K4-432AXSP04	347.10	569	427.4	486.5	976	354	569.6	430.2	487	966.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K4-525AXSP04	417.90	673.8	511.1	577.5	1133.6	425.8	671.9	512.5	576.8	1120.8	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K4-532AXSP04	389.40	634.7	479.2	543.6	1077.1	397.5	634.6	481.4	543.6	1065.3	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K4-625AXSP06	487.00	746.6	576.5	644.2	-	487.8	740.4	573.3	639.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K4-632AXSP06	461.80	714.6	548.7	615.6	-	463.1	708.9	546.1	611.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K5-425AXSP04	378.00	611.8	462.1	523.5	-	384.3	612.3	464	524	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K5-432AXSP04	347.10	569	427.4	486.5	976	354	569.6	430.2	487	966.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K5-525AXSP04	417.90	673.8	511.1	577.5	1133.6	425.8	671.9	512.5	576.8	1120.8	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K5-532AXSP04	389.40	634.7	479.2	543.6	1077.1	397.5	634.6	481.4	543.6	1065.3	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K5-625AXSP06	487.00	746.6	576.5	644.2	-	487.8	740.4	573.3	639.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K5-632AXSP06	461.80	714.6	548.7	615.6	-	463.1	708.9	546.1	611.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K8-425AXSP04	378.00	611.8	462.1	523.5	-	384.3	612.3	464	524	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K8-432AXSP04	347.10	569	427.4	486.5	976	354	569.6	430.2	487	966.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K8-525AXSP04	417.90	673.8	511.1	577.5	1133.6	425.8	671.9	512.5	576.8	1120.8	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K8-532AXSP04	389.40	634.7	479.2	543.6	1077.1	397.5	634.6	481.4	543.6	1065.3	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K8-625AXSP06	487.00	746.6	576.5	644.2	-	487.8	740.4	573.3	639.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K8-632AXSP06	461.80	714.6	548.7	615.6	-	463.1	708.9	546.1	611.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K9-425AXSP04	378.00	611.8	462.1	523.5	-	384.3	612.3	464	524	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K9-432AXSP04	347.10	569	427.4	486.5	976	354	569.6	430.2	487	966.4	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550K9-525AXSP04	417.90	673.8	511.1	577.5	1133.6	425.8	671.9	512.5	576.8	1120.8	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K9-532AXSP04	389.40	634.7	479.2	543.6	1077.1	397.5	634.6	481.4	543.6	1065.3	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550K9-625AXSP06	487.00	746.6	576.5	644.2	-	487.8	740.4	573.3	639.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550K9-632AXSP06	461.80	714.6	548.7	615.6	-	463.1	708.9	546.1	611.4	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB550R3-425AXSP04	388.20	629.5	474.1	538.3	-	395	629.4	476.3	538.2	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550R3-432AXSP04	356.70	585.3	439.3	499.1	1003.6	363.6	585.2	442.1	499.9	994.1	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB550R3-525AXSP04	430.00	692.2	525.4	592.9	1165.7	437.7	691.6	527.1	593.4	1153.1	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550R3-532AXSP04	399.90	652.9	492.4	558	1109.1	408.5	652.1	495	558.3	1097.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB550R3-625AXSP04	463.00	740.8	564	636.7	1233.1	472.1	739.5	566	636.5	1218.6	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB550R3-632AXSP06	474.60	734.3	564.2	632.3	-	475.5	728.7	561.7	628.2	-	609	30.8	4"	487	23.4	3"	730	43.2	4"
EAW-VD1556ZB750C2-425AXSP04	423.00	685.5	515.9	585.7	-	429.6	686.1	519	586.3	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C2-432AXSP04	388.20	635.7	476.3	541.6	-	395.5	635	479.3	543.1	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C2-525AXSP04	470.90	757.1	572.6	648.3	-	479.5	756.3	576.4	648.7	-	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C2-532AXSP04	436.60	711	536	608.3	1212.4	445.2	710.9	539.4	608.3	1200.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C2-625AXSP04	507.60	812.1	618.4	696.8	1356.5	517.4	811.2	621	697.1	1341.1	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C2-632AXSP04	478.10	773.3	585.5	663.1	1304.9	488	773.2	588.9	663.1	1291.7	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C3-425AXSP04	423.00	685.5	515.9	585.7	-	429.6	686.1	519	586.3	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C3-432AXSP04	388.20	635.7	476.3	541.6	-	395.5	635	479.3	543.1	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C3-525AXSP04	470.90	757.1	572.6	648.3	-	479.5	756.3	576.4	648.7	-	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C3-532AXSP04	436.60	711	536	608.3	1212.4	445.2	710.9	539.4	608.3	1200.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C3-625AXSP04	507.60	812.1	618.4	696.8	1356.5	517.4	811.2	621	697.1	1341.1	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C3-632AXSP04	478.10	773.3	585.5	663.1	1304.9	488	773.2	588.9	663.1	1291.7	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C4-425AXSP04	423.00	685.5	515.9	585.7	-	429.6	686.1	519	586.3	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C4-432AXSP04	388.20	635.7	476.3	541.6	-	395.5	635	479.3	543.1	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C4-525AXSP04	470.90	757.1	572.6	648.3	-	479.5	756.3	576.4	648.7	-	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C4-532AXSP04	436.60	711	536	608.3	1212.4	445.2	710.9	539.4	608.3	1200.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C4-625AXSP04	507.60	812.1	618.4	696.8	1356.5	517.4	811.2	621	697.1	1341.1	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C4-632AXSP04	478.10	773.3	585.5	663.1	1304.9	488	773.2	588.9	663.1	1291.7	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C5-425AXSP04	423.00	685.5	515.9	585.7	-	429.6	686.1	519	586.3	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C5-432AXSP04	388.20	635.7	476.3	541.6	-	395.5	635	479.3	543.1	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C5-525AXSP04	470.90	757.1	572.6	648.3	-	479.5	756.3	576.4	648.7	-	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C5-532AXSP04	436.60	711	536	608.3	1212.4	445.2	710.9	539.4	608.3	1200.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C5-625AXSP04	507.60	812.1	618.4	696.8	1356.5	517.4	811.2	621	697.1	1341.1	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C5-632AXSP04	478.10	773.3	585.5	663.1	1304.9	488	773.2	588.9	663.1	1291.7	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750C8-425AXSP04	423.00	685.5	515.9	585.7	-	429.6	686.1	519	586.3	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C8-432AXSP04	388.20	635.7	476.3	541.6	-	395.5	635	479.3	543.1	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750C8-525AXSP04	470.90	757.1	572.6	648.3	-	479.5	756.3	576.4	648.7	-	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C8-532AXSP04	436.60	711	536	608.3	1212.4	445.2	710.9	539.4	608.3	1200.4	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750C8-625AXSP04	507.60	812.1	618.4	696.8	1356.5	517.4	811.2	621	697.1	1341.1	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB7																			

EAW-VD1556ZB750K9-525AXSP04	454.10	729.7	553.5	625.3	1232.8	462	729.6	555.9	626.3	1220.2	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750K9-532AXSP04	421.90	687.7	518.3	587.9	1169.1	430.7	687.5	521.6	588.8	1157.6	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750K9-625AXSP04	488.40	781	595.4	670.6	1303.4	498.6	780.5	598.1	671.1	1289.2	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750K9-632AXSP04	460.40	746.6	565.2	639.8	1256.7	470.3	746.1	568.2	640.4	1243.5	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750R3-425AXSP04	400.70	648.8	488.7	554.2	-	407.3	649.1	491.4	555.6	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750R3-432AXSP04	368.10	603.2	452.9	514.8	-	375.3	603.6	455.3	515.2	-	609	21.3	4"	487	17.1	3"	730	29.9	4"
EAW-VD1556ZB750R3-525AXSP04	443.30	713.7	541.1	611	1203.2	451.7	713.6	543.3	611.9	1190.9	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750R3-532AXSP04	413.20	672.6	507.4	575.2	1144.1	421	672.3	510.5	576	1132.7	755	22.5	4"	604	14.8	4"	906	27.8	(2) 4"
EAW-VD1556ZB750R3-625AXSP04	476.90	762.8	580.3	655.3	1270.6	486	761.1	583.7	654.7	1256.6	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZB750R3-632AXSP04	450.30	729.4	551.7	625.3	1226.8	459.9	728.8	554.5	625.8	1213.8	913	20.3	(2) 4"	730	15.9	4"	1096	28.4	(2) 4"
EAW-VD1556ZK017G7-425AXSP02	-	764.4	538.4	636.7	1380.5	430.5	780.7	561.3	653.3	1376.8	1217	12.8	(2) 4"	974	8.4	(2) 4"	1461	17.9	(2) 4"
EAW-VD1556ZK017G7-432AXSP04	489.50	794.8	596.8	678.2	-	495.7	793.8	598.7	677.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK017G7-525AXSP04	605.00	965.5	731.9	827.3	-	612.4	963.5	733.7	825.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK017G7-532AXSP04	559.10	899.5	678.6	768.9	-	565.5	897.3	680.3	768.4	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK017G7-625AXSP04	663.90	1048.2	798.8	900.1	-	671.8	1044.4	800.2	898.1	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK017G7-632AXSP04	620.40	987.5	749.5	846.2	-	627.3	984.9	750.8	845.3	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK370C2-425AXSP04	374.60	598.6	454.5	513.3	1011	378.4	596.2	454.7	511.3	996.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370C2-432AXSP04	344.50	557.1	421	476.7	946.9	349.2	554.9	421.3	475.6	935.2	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370C2-525AXSP04	414.70	658.4	502.3	565.4	1096.9	419.3	654.6	502	562.9	1081.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370C2-532AXSP04	386.10	621.2	470.6	532.4	1043.6	391.5	618.2	471.1	530.6	1029.6	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370C2-625AXSP04	446.20	702.8	537.9	605.8	1158	452	699.1	537.7	602.7	1141.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK370C2-632AXSP06	454.10	694.6	536.5	600	-	453.2	687.2	532.3	593.4	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370C4-425AXSP04	374.60	598.6	454.5	513.3	1011	378.4	596.2	454.7	511.3	996.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370C4-432AXSP04	344.50	557.1	421	476.7	946.9	349.2	554.9	421.3	475.6	935.2	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370C4-525AXSP04	414.70	658.4	502.3	565.4	1096.9	419.3	654.6	502	562.9	1081.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370C4-532AXSP04	386.10	621.2	470.6	532.4	1043.6	391.5	618.2	471.1	530.6	1029.6	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370C4-625AXSP04	446.20	702.8	537.9	605.8	1158	452	699.1	537.7	602.7	1141.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK370C4-632AXSP06	454.10	694.6	536.5	600	-	453.2	687.2	532.3	593.4	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370C5-425AXSP04	374.60	598.6	454.5	513.3	1011	378.4	596.2	454.7	511.3	996.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370C5-432AXSP04	344.50	557.1	421	476.7	946.9	349.2	554.9	421.3	475.6	935.2	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370C5-525AXSP04	414.70	658.4	502.3	565.4	1096.9	419.3	654.6	502	562.9	1081.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370C5-532AXSP04	386.10	621.2	470.6	532.4	1043.6	391.5	618.2	471.1	530.6	1029.6	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370C5-625AXSP04	446.20	702.8	537.9	605.8	1158	452	699.1	537.7	602.7	1141.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK370C5-632AXSP06	454.10	694.6	536.5	600	-	453.2	687.2	532.3	593.4	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K2-425AXSP04	360.50	576.7	437.8	494.2	971.4	364.8	574.5	438	493.1	959.1	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K2-432AXSP04	332.60	538.5	406.9	460.4	913.9	337	536.2	407.1	459.2	902.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K2-525AXSP04	397.50	631.8	481.9	543	1051.5	402.6	628.3	481.7	540.7	1036.3	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K2-532AXSP04	371.40	598.1	453.1	513.1	1003.7	377.2	595.4	453.6	511.5	990.5	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K2-625AXSP06	458.90	694.6	538.7	601	-	457.6	686.5	534.5	594.5	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K2-632AXSP06	436.40	666.6	515.3	576.1	-	435.6	659.6	511.4	569.9	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K4-425AXSP04	360.50	576.7	437.8	494.2	971.4	364.8	574.5	438	493.1	959.1	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K4-432AXSP04	332.60	538.5	406.9	460.4	913.9	337	536.2	407.1	459.2	902.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K4-525AXSP04	397.50	631.8	481.9	543	1051.5	402.6	628.3	481.7	540.7	1036.3	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K4-532AXSP04	371.40	598.1	453.1	513.1	1003.7	377.2	595.4	453.6	511.5	990.5	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K4-625AXSP06	458.90	694.6	538.7	601	-	457.6	686.5	534.5	594.5	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K4-632AXSP06	436.40	666.6	515.3	576.1	-	435.6	659.6	511.4	569.9	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K5-425AXSP04	360.50	576.7	437.8	494.2	971.4	364.8	574.5	438	493.1	959.1	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K5-432AXSP04	332.60	538.5	406.9	460.4	913.9	337	536.2	407.1	459.2	902.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K5-525AXSP04	397.50	631.8	481.9	543	1051.5	402.6	628.3	481.7	540.7	1036.3	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K5-532AXSP04	371.40	598.1	453.1	513.1	1003.7	377.2	595.4	453.6	511.5	990.5	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K5-625AXSP06	458.90	694.6	538.7	601	-	457.6	686.5	534.5	594.5	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K5-632AXSP06	436.40	666.6	515.3	576.1	-	435.6	659.6	511.4	569.9	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K8-425AXSP04	360.50	576.7	437.8	494.2	971.4	364.8	574.5	438	493.1	959.1	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K8-432AXSP04	332.60	538.5	406.9	460.4	913.9	337	536.2	407.1	459.2	902.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK370K8-525AXSP04	397.50	631.8	481.9	543	1051.5	402.6	628.3	481.7	540.7	1036.3	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K8-532AXSP04	371.40	598.1	453.1	513.1	1003.7	377.2	595.4	453.6	511.5	990.5	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK370K8-625AXSP06	458.90	694.6	538.7	601	-	457.6	686.5	534.5	594.5	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK370K8-632AXSP06	436.40	666.6	515.3	576.1	-	435.6	659.6	511.4	569.9	-	609	33.8	4"	487	25.4	3"	730	47.4	4"
EAW-VD1556ZK400B3-425AXSP04	365.50	585.2	444	501.3	986.1	370	582.2	444.3	499.6	973.8	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK400B3-432AXSP04	336.90	545.9	412.3	466.6	926.9	341.4	543.7	412.5	465.5	914.2	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK400B3-525AXSP04	403.60	641	488.7	550.7	1067.1	408.9	637.6	488.6	548.5	1051.8	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK400B3-532AXSP04	377.10	606	459.5																

EAW-VD1556ZK5S083-432AXSP04	371.60	601	453.5	514.1	-	376.9	599.5	454.5	512.8	1011.9	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S083-525AXSP04	447.60	709.9	541	609.6	1186.5	452.8	707	541.7	608	1170.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S083-532AXSP04	417.20	669.7	508.4	573.9	1128.1	423.1	667.5	508.9	573	1114.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S083-625AXSP04	481.10	757.8	580.5	652.5	1251.9	487.5	754	581.2	650.1	1235.2	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S083-632AXSP04	455.00	725.9	552	623.3	1209.4	461.4	722.5	553.2	621.3	1194.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C2-425AXSP04	421.90	674.3	510.3	577.6	-	426.2	672.6	511.4	576.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C2-432AXSP04	387.30	625.7	472.1	534.6	-	391.9	623.8	472.1	533.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C2-525AXSP04	469.70	745.5	567.3	639.6	1247.9	474.9	742	567.7	637.6	1231.8	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C2-532AXSP04	436.40	700.1	531.4	600.3	1181.2	441.9	697.6	531.8	598.2	1166.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C2-625AXSP04	508.40	800	612.9	688.4	1323.3	514.3	795.6	612.5	685.5	1306.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C2-632AXSP04	478.00	762.2	580.4	654.8	1273.1	484.5	758.2	580.5	652.3	1254.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C3-425AXSP04	421.90	674.3	510.3	577.6	-	426.2	672.6	511.4	576.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C3-432AXSP04	387.30	625.7	472.1	534.6	-	391.9	623.8	472.1	533.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C3-525AXSP04	469.70	745.5	567.3	639.6	1247.9	474.9	742	567.7	637.6	1231.8	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C3-532AXSP04	436.40	700.1	531.4	600.3	1181.2	441.9	697.6	531.8	598.2	1166.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C3-625AXSP04	508.40	800	612.9	688.4	1323.3	514.3	795.6	612.5	685.5	1306.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C3-632AXSP04	478.00	762.2	580.4	654.8	1273.1	484.5	758.2	580.5	652.3	1254.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C4-425AXSP04	421.90	674.3	510.3	577.6	-	426.2	672.6	511.4	576.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C4-432AXSP04	387.30	625.7	472.1	534.6	-	391.9	623.8	472.1	533.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C4-525AXSP04	469.70	745.5	567.3	639.6	1247.9	474.9	742	567.7	637.6	1231.8	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C4-532AXSP04	436.40	700.1	531.4	600.3	1181.2	441.9	697.6	531.8	598.2	1166.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C5-625AXSP04	508.40	800	612.9	688.4	1323.3	514.3	795.6	612.5	685.5	1306.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C5-632AXSP04	478.00	762.2	580.4	654.8	1273.1	484.5	758.2	580.5	652.3	1254.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C8-425AXSP04	421.90	674.3	510.3	577.6	-	426.2	672.6	511.4	576.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C8-432AXSP04	387.30	625.7	472.1	534.6	-	391.9	623.8	472.1	533.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C8-425AXSP04	469.70	745.5	567.3	639.6	1247.9	474.9	742	567.7	637.6	1231.8	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C8-525AXSP04	436.40	700.1	531.4	600.3	1181.2	441.9	697.6	531.8	598.2	1166.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C8-532AXSP04	508.40	800	612.9	688.4	1323.3	514.3	795.6	612.5	685.5	1306.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C9-425AXSP04	421.90	674.3	510.3	577.6	-	426.2	672.6	511.4	576.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C9-432AXSP04	387.30	625.7	472.1	534.6	-	391.9	623.8	472.1	533.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0C9-525AXSP04	469.70	745.5	567.3	639.6	1247.9	474.9	742	567.7	637.6	1231.8	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C9-532AXSP04	436.40	700.1	531.4	600.3	1181.2	441.9	697.6	531.8	598.2	1166.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0C9-625AXSP04	508.40	800	612.9	688.4	1323.3	514.3	795.6	612.5	685.5	1306.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0C9-632AXSP04	478.00	762.2	580.4	654.8	1273.1	484.5	758.2	580.5	652.3	1254.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K2-425AXSP04	405.10	646.9	490.5	554.7	-	409.3	645.4	490.7	553.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K2-432AXSP04	372.70	602.3	454.4	515.2	-	377.7	600.9	455.6	514	1014.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K2-525AXSP04	448.40	711.3	542	610.7	1189	454.2	708.3	542.7	609.1	1174.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K2-532AXSP04	417.90	671.1	509.3	575.9	1132.1	423.9	668.9	509.9	574.1	1116.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K2-625AXSP04	482.80	761.4	582.5	654.8	1256.5	489	757.3	583	653	1239.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K2-632AXSP04	455.80	727.3	553.9	625.3	1213.4	462.8	723.9	554.2	623.3	1196.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K3-425AXSP04	405.10	646.9	490.5	554.7	-	409.3	645.4	490.7	553.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K3-432AXSP04	372.70	602.3	454.4	515.2	-	377.7	600.9	455.6	514	1014.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K3-525AXSP04	448.40	711.3	542	610.7	1189	454.2	708.3	542.7	609.1	1174.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K3-532AXSP04	417.90	671.1	509.3	575.9	1132.1	423.9	668.9	509.9	574.1	1116.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K3-625AXSP04	482.80	761.4	582.5	654.8	1256.5	489	757.3	583	653	1239.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K3-632AXSP04	455.80	727.3	553.9	625.3	1213.4	462.8	723.9	554.2	623.3	1196.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K4-425AXSP04	405.10	646.9	490.5	554.7	-	409.3	645.4	490.7	553.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K4-432AXSP04	372.70	602.3	454.4	515.2	-	377.7	600.9	455.6	514	1014.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K4-525AXSP04	448.40	711.3	542	610.7	1189	454.2	708.3	542.7	609.1	1174.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K4-532AXSP04	417.90	671.1	509.3	575.9	1132.1	423.9	668.9	509.9	574.1	1116.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K4-625AXSP04	482.80	761.4	582.5	654.8	1256.5	489	757.3	583	653	1239.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K4-632AXSP04	455.80	727.3	553.9	625.3	1213.4	462.8	723.9	554.2	623.3	1196.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K5-425AXSP04	405.10	646.9	490.5	554.7	-	409.3	645.4	490.7	553.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K5-432AXSP04	372.70	602.3	454.4	515.2	-	377.7	600.9	455.6	514	1014.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K5-525AXSP04	448.40	711.3	542	610.7	1189	454.2	708.3	542.7	609.1	1174.4	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K5-532AXSP04	417.90	671.1	509.3	575.9	1132.1	423.9	668.9	509.9	574.1	1116.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK5S0K5-625AXSP04	482.80	761.4	582.5	654.8	1256.5	489	757.3	583	653	1239.3	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K5-632AXSP04	455.80	727.3	553.9	625.3	1213.4	462.8	723.9	554.2	623.3	1196.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK5S0K8-425AXSP04	405.10	646.9	490.5	554.7	-	409.3	645.4	490.7	553.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K8-432AXSP04	372.70	602.3	454.4	515.2	-	377.7	600.9	455.6	514	1014.5	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK5S0K8-525AXSP04	448.40	711.3	542	610.7	1189	454.2	708.3	542.7	609.1	1174.4	755	24.5	4"	604	16.1				

EAW-VD1556ZK750C5-425AXSP04	453.30	726.8	549.2	621.4	-	458.1	724.8	550.3	620.8	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750C5-432AXSP04	416.70	673.2	507.1	575	-	421.6	671.3	508	574.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750C5-525AXSP04	505.60	802	610.5	688	-	511.6	799.7	611.2	687	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750C5-532AXSP04	470.40	754.3	570.8	645.6	-	476.4	751.6	572.2	644.3	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750C5-625AXSP04	546.90	860.8	659	740.7	1429.5	554.4	857.5	659.8	738.9	1411.6	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750C5-632AXSP04	515.20	820.7	624.4	704	1373.9	521.7	817.8	625.7	702.6	1356.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750C8-425AXSP04	453.30	726.8	549.2	621.4	-	458.1	724.8	550.3	620.8	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750C8-432AXSP04	416.70	673.2	507.1	575	-	421.6	671.3	508	574.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750C8-525AXSP04	505.60	802	610.5	688	-	511.6	799.7	611.2	687	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750C8-532AXSP04	470.40	754.3	570.8	645.6	-	476.4	751.6	572.2	644.3	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750C8-625AXSP04	546.90	860.8	659	740.7	1429.5	554.4	857.5	659.8	738.9	1411.6	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750C8-632AXSP04	515.20	820.7	624.4	704	1373.9	521.7	817.8	625.7	702.6	1356.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750C9-425AXSP04	453.30	726.8	549.2	621.4	-	458.1	724.8	550.3	620.8	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750C9-432AXSP04	416.70	673.2	507.1	575	-	421.6	671.3	508	574.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750C9-525AXSP04	505.60	802	610.5	688	-	511.6	799.7	611.2	687	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750C9-532AXSP04	470.40	754.3	570.8	645.6	-	476.4	751.6	572.2	644.3	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750C9-625AXSP04	546.90	860.8	659	740.7	1429.5	554.4	857.5	659.8	738.9	1411.6	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750C9-632AXSP04	515.20	820.7	624.4	704	1373.9	521.7	817.8	625.7	702.6	1356.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K2-425AXSP04	438.40	702.6	531.7	601.2	-	443.8	700.9	532.8	600.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K2-432AXSP04	404.50	653.1	491.7	558.4	-	409.6	651.4	493.7	557.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K2-525AXSP04	488.30	774.1	589.2	664.6	-	493.9	771.8	589.8	662.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K2-532AXSP04	454.60	728.7	552.2	624.2	1231.3	460.4	727.4	553.6	623.1	1217.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K2-625AXSP04	526.40	829.5	634.9	713.3	1373	533.3	826	635.4	711.3	1355.4	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K2-632AXSP04	496.80	791.2	602.7	679.2	1323.1	503.7	788.4	603.8	677.8	1306	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K3-425AXSP04	438.40	702.6	531.7	601.2	-	443.8	700.9	532.8	600.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K3-432AXSP04	404.50	653.1	491.7	558.4	-	409.6	651.4	493.7	557.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K3-525AXSP04	488.30	774.1	589.2	664.6	-	493.9	771.8	589.8	662.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K3-532AXSP04	454.60	728.7	552.2	624.2	1231.3	460.4	727.4	553.6	623.1	1217.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K3-625AXSP04	526.40	829.5	634.9	713.3	1373	533.3	826	635.4	711.3	1355.4	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K3-632AXSP04	496.80	791.2	602.7	679.2	1323.1	503.7	788.4	603.8	677.8	1306	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K4-425AXSP04	438.40	702.6	531.7	601.2	-	443.8	700.9	532.8	600.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K4-432AXSP04	404.50	653.1	491.7	558.4	-	409.6	651.4	493.7	557.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K4-525AXSP04	488.30	774.1	589.2	664.6	-	493.9	771.8	589.8	662.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K4-532AXSP04	454.60	728.7	552.2	624.2	1231.3	460.4	727.4	553.6	623.1	1217.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K4-625AXSP04	526.40	829.5	634.9	713.3	1373	533.3	826	635.4	711.3	1355.4	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K4-632AXSP04	496.80	791.2	602.7	679.2	1323.1	503.7	788.4	603.8	677.8	1306	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K5-425AXSP04	438.40	702.6	531.7	601.2	-	443.8	700.9	532.8	600.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K5-432AXSP04	404.50	653.1	491.7	558.4	-	409.6	651.4	493.7	557.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K5-525AXSP04	488.30	774.1	589.2	664.6	-	493.9	771.8	589.8	662.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K5-532AXSP04	454.60	728.7	552.2	624.2	1231.3	460.4	727.4	553.6	623.1	1217.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K5-625AXSP04	526.40	829.5	634.9	713.3	1373	533.3	826	635.4	711.3	1355.4	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K5-632AXSP04	496.80	791.2	602.7	679.2	1323.1	503.7	788.4	603.8	677.8	1306	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K8-425AXSP04	438.40	702.6	531.7	601.2	-	443.8	700.9	532.8	600.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K8-432AXSP04	404.50	653.1	491.7	558.4	-	409.6	651.4	493.7	557.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K8-525AXSP04	488.30	774.1	589.2	664.6	-	493.9	771.8	589.8	662.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K8-532AXSP04	454.60	728.7	552.2	624.2	1231.3	460.4	727.4	553.6	623.1	1217.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K8-625AXSP04	526.40	829.5	634.9	713.3	1373	533.3	826	635.4	711.3	1355.4	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K8-632AXSP04	496.80	791.2	602.7	679.2	1323.1	503.7	788.4	603.8	677.8	1306	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K9-425AXSP04	438.40	702.6	531.7	601.2	-	443.8	700.9	532.8	600.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K9-432AXSP04	404.50	653.1	491.7	558.4	-	409.6	651.4	493.7	557.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750K9-525AXSP04	488.30	774.1	589.2	664.6	-	493.9	771.8	589.8	662.6	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K9-532AXSP04	454.60	728.7	552.2	624.2	1231.3	460.4	727.4	553.6	623.1	1217.7	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750K9-625AXSP04	526.40	829.5	634.9	713.3	1373	533.3	826	635.4	711.3	1355.4	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750K9-632AXSP04	496.80	791.2	602.7	679.2	1323.1	503.7	788.4	603.8	677.8	1306	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750R3-425AXSP04	429.40	688.4	520.6	588.4	-	434.6	686.6	521.6	587.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750R3-432AXSP04	396.00	639.7	482.1	546.3	-	401.5	637.9	484	546.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD1556ZK750R3-525AXSP04	476.70	756.2	576	649.5	-	482.9	753.9	576.5	647.5	1252	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750R3-532AXSP04	444.40	713.8	540.5	610.8	1205.1	450.8	711.3	541.8	609.7	1190.1	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD1556ZK750R3-625AXSP04	514.20	809.5	620	696.4	1339.1	520.8	806	620.4	694.3	1322.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD1556ZK750R3-632AXSP04	485.10	773	589.2	663.8	1291.9	491.8	770.2	590.3	662.4	1276.8	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9102PA177F7-425AXSP16	-	50.4	-	41.2	95.2	-	52.5	-	43.5	95.5	113	15.8	1-1/2"	90	10.4	1-1/2"	135	22.2	1-1/2"
EAW-VD9102PA177F7-432AXSP16	-	46.6	-	37.9	89.4	-	48.7	-	40.2	89.6	113	15.8	1-1/2"	90	10.4	1-1/2"</			



EAW-VD9102PJ320P5-632AXSP16	-	74.1	-	61.2	136.3	-	76.4	-	63.8	136.3	169	15.9	2"	135	13.8	1-1/2"	203	22.4	2"
EAW-VD9102PJ320P7-425AXSP16	-	67.9	47.2	56.3	124.1	-	69.8	49.7	58.2	124.2	113	16.7	1-1/2"	90	11	1-1/2"	135	23.4	1-1/2"
EAW-VD9102PJ320P7-432AXSP16	-	62.3	42.9	51.5	115.2	-	64.1	45.4	53.3	115.3	113	16.7	1-1/2"	90	11	1-1/2"	135	23.4	1-1/2"
EAW-VD9102PJ320P7-525AXSP16	-	73.3	50.9	60.8	133.5	-	75.4	53.9	62.9	133.5	135	18.2	1-1/2"	108	12	1-1/2"	162	21	2"
EAW-VD9102PJ320P7-532AXSP16	-	68.1	46.9	56.2	125.7	-	70.2	49.9	58.4	125.8	135	18.2	1-1/2"	108	12	1-1/2"	162	21	2"
EAW-VD9102PJ320P7-625AXSP16	-	79.8	-	66.1	144.8	-	82.2	59	68.8	144.6	169	15.9	2"	135	13.8	1-1/2"	203	22.4	2"
EAW-VD9102PJ320P7-632AXSP16	-	75.3	-	62.2	138.4	-	77.7	-	64.9	138.5	169	15.9	2"	135	13.8	1-1/2"	203	22.4	2"
EAW-VD9102ZA177F7-425AXSP16	-	56.8	-	-	108.4	-	59.2	-	49	108.5	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA177F7-432AXSP16	-	52.2	-	-	101.4	-	54.8	-	-	101.4	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA177F7-525AXSP16	-	61.5	-	-	117.4	-	64.4	-	-	117.4	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA177F7-532AXSP16	-	-	-	-	111.4	-	60.5	-	-	111.3	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA177F7-625AXSP16	-	-	-	-	125.6	-	-	-	-	125.4	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA177F7-632AXSP16	-	-	-	-	121.1	-	-	-	-	121	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA24716-425AXSP16	-	62.4	-	50.9	118.3	-	64.9	-	53.7	118.5	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA24716-432AXSP16	-	57.3	-	-	110.4	-	59.9	-	49.4	110.6	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA24716-525AXSP16	-	67.8	-	-	128.7	-	70.9	-	-	128.6	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA24716-532AXSP16	-	63.2	-	-	121.8	-	66.3	-	-	121.9	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA24716-625AXSP16	-	-	-	-	138.2	-	76.6	-	-	138.2	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA24716-632AXSP16	-	-	-	-	133	-	-	-	-	133	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA320P5-425AXSP16	-	68.6	-	56.1	129.6	-	71.2	49.7	58.9	129.5	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA320P5-432AXSP16	-	62.7	-	51	120	-	65.2	-	53.8	120.2	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA320P5-525AXSP16	-	75.3	-	61.6	142.1	-	78.4	-	65	142	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA320P5-532AXSP16	-	69.8	-	-	133.6	-	72.9	-	-	133.7	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA320P5-625AXSP16	-	82.1	-	-	154.6	-	85.6	-	-	154.3	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA320P5-632AXSP16	-	77	-	-	147.5	-	80.7	-	-	147.3	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA320P7-425AXSP16	-	70	-	57.3	131.9	-	72.6	50.7	60.1	132	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA320P7-432AXSP16	-	63.9	-	52.1	122.3	-	66.6	-	54.9	122.5	146	14.5	2"	117	12.2	1-1/2"	176	20.4	2"
EAW-VD9102ZA320P7-525AXSP16	-	76.8	-	62.9	144.6	-	79.9	-	66.2	144.8	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA320P7-532AXSP16	-	71.1	-	-	136	-	74.2	-	61.3	136.2	180	15.6	2"	144	10.3	2"	216	22	2"
EAW-VD9102ZA320P7-625AXSP16	-	83.6	-	-	157.3	-	87.2	-	-	157.1	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZA320P7-632AXSP16	-	78.5	-	-	150.3	-	82.3	-	-	150.1	225	17.5	2"	180	11.5	2"	270	18.6	3"
EAW-VD9102ZJ177F7-425AXSP16	-	61.8	-	51	114.7	-	63.8	-	53.2	114.5	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ177F7-432AXSP16	-	57.1	-	-	107.3	-	59.1	-	49	107.2	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ177F7-525AXSP16	-	67.3	-	-	124.6	-	69.6	-	-	124.1	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ177F7-532AXSP16	-	62.9	-	-	118.2	-	65.3	-	-	117.8	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ177F7-625AXSP16	-	-	-	-	133.2	-	-	-	-	132.7	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ177F7-632AXSP16	-	-	-	-	128.5	-	-	-	-	128	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ24716-425AXSP16	-	68.1	-	56.2	125.8	-	70	49.8	58.4	125.5	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ24716-432AXSP16	-	62.6	-	51.5	117.3	-	64.6	-	53.7	117.1	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ24716-525AXSP16	-	74.3	-	61.2	136.7	-	76.5	-	63.9	136.2	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ24716-532AXSP16	-	69.3	-	-	129.6	-	71.7	-	-	129.3	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ24716-625AXSP16	-	80.2	-	-	147.2	-	82.9	-	-	146.6	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ24716-632AXSP16	-	75.9	-	-	141.4	-	78.9	-	-	141.1	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ320P5-425AXSP16	-	74.5	51.4	61.6	137.2	-	76.6	54.5	63.8	136.9	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ320P5-432AXSP16	-	68.2	-	56.2	127.2	-	70.3	49.7	58.5	127	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ320P5-525AXSP16	-	82.2	-	67.9	150.7	-	84.4	60.2	70.6	150.1	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ320P5-532AXSP16	-	76.1	-	62.7	141.5	-	78.5	-	65.3	141.2	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ320P5-625AXSP16	-	89.6	-	-	163.7	-	92.3	-	77.2	162.9	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ320P5-632AXSP16	-	84.2	-	-	156.3	-	87.1	-	-	155.6	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ320P7-425AXSP16	-	76.1	52.5	63	140	-	78.1	55.7	65.2	139.8	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ320P7-432AXSP16	-	69.7	-	57.4	129.8	-	71.8	50.8	59.6	129.6	146	15.4	2"	117	12.8	1-1/2"	176	21.6	2"
EAW-VD9102ZJ320P7-525AXSP16	-	83.7	-	69.3	153.5	-	86.1	61.5	72	153	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ320P7-532AXSP16	-	77.6	-	64	144.4	-	80.2	-	66.7	144.1	180	16.5	2"	144	10.9	2"	216	23.2	2"
EAW-VD9102ZJ320P7-625AXSP16	-	91.4	-	75.6	167	-	94.2	-	78.8	166.2	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9102ZJ320P7-632AXSP16	-	86	-	-	159.3	-	88.9	-	-	158.9	225	18.3	2"	180	12.1	2"	270	19.9	3"
EAW-VD9104PA177F7-425AXSP16	71.60	117.5	88.1	100.3	-	73.4	118	89	100.8	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD9104PA177F7-432AXSP16	66.00	109.6	81.9	93.4	-	67.7	110.1	82.8	93.8	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD9104PA177F7-525AXSP16	76.90	125.7	94.8	107.6	214.1	79	126.3	95.8	108.1	212.8	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD9104PA177F7-532AXSP16	71.90	119.1	89.4	101.6	204.4	74.1	119.6	90.4	102.3	202.9	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD9104PA177F7-625AXSP16	83.40	135.6	102.6	116.3	227.5	85.8	136.1	103.7	116.9	226.1	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD9104PA177F7-632AXSP16	79.30	130.7	98.2	111.8	221.6	81.7	131.2	99.4	112.5	219.9	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD9104PA24716-425AXSP16	77.60	127.2	95.3	108.5	-	79.4	128	96.4	109.2	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD9104PA24716-432AXSP16	71.50	118.5	88.4	100.9	-	73.3	119.2	89.5	101.5	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD9104PA24716-525AXSP16	83.90	136.8	103	116.9	-	86	137.4	104	117.6	-	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD9104PA24716-532AXSP16	78.10	129.1	96.7	109.9	221.7	80.2	129.6	97.7	110.8	220.6	135	25.3	1-1/2"	108	16.6	1-1/2"	162	30.9	2"
EAW-VD9104PA24716-625AXSP16	91.30	148.1	112.2	126.8	249.4	93.8	148.7	113.3	127.6	247.7	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD9104PA24716-632AXSP16	86.50	142.2	107	121.7	241.6	89	142.8	108.2	122.2	240.1	169	23	2"	135	18.4	1-1/2"	203	32.3	2"
EAW-VD9104PA320P5-425AXSP16	85.10	139.9	104.6	119.2	-	87	140.8	105.8	120	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD9104PA320P5-432AXSP16	78.10	129.3	96.4	110.1	-	79.9	130	97.5	110.8	-	113	23.7	1-1/2"	90	15.7	1-1/2"	135	33.4	1-1/2"
EAW-VD9104PA320P5-525AXSP16	93.00	151.5</																	

EAW-VD9104P1320P7-625AXSP16	113.70	180.8	137.3	155.1	-	115.6	181.2	138.2	155.4	-	169	24.8	2"	135	19.6	1-1/2"	203	34.8	2"
EAW-VD9104P1320P7-632AXSP16	106.80	171.8	129.9	147	-	108.8	172.1	130.9	147.5	-	169	24.8	2"	135	19.6	1-1/2"	203	34.8	2"
EAW-VD9104Z177F7-425AXSP16	81.30	134	100.7	114.4	229.6	83.3	134.2	101.4	114.7	227.7	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z177F7-432AXSP16	74.60	124.7	93.1	106.3	215.2	76.6	125	93.9	106.7	213.2	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z177F7-525AXSP16	89.20	146.5	110.5	125.4	248.4	91.6	146.7	111.3	125.8	245.9	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z177F7-532AXSP16	83.00	138.4	103.4	118.1	236.5	85.4	138.5	104.4	118.4	234.1	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z177F7-625AXSP16	97.40	159.2	120	136.1	265.9	100.1	159.1	121	136.4	263.1	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z177F7-632AXSP16	92.00	152.4	114.2	130	257.4	94.9	152.7	115.3	130.5	254.7	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z24716-425AXSP16	88.70	146	109.5	124.5	-	90.9	146.3	110.5	124.9	-	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z24716-432AXSP16	81.30	135.4	101.3	115.4	234.4	83.5	135.9	102.2	115.9	232.5	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z24716-525AXSP16	97.90	160	120.8	136.9	272.3	100.3	160.5	121.7	137.5	269.7	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z24716-532AXSP16	90.80	150.7	113	128.6	258.2	93.3	151.1	114.1	129.2	255.9	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z24716-625AXSP16	107.00	174.4	131.8	149.6	292.3	110.1	174.6	132.9	150	289.6	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z24716-632AXSP16	100.80	166.7	125.1	142.3	282	103.9	167	126.2	143	279.5	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z320P5-425AXSP16	97.10	159.6	119.3	135.9	-	99.2	159.8	120.4	136.4	-	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z320P5-432AXSP16	88.50	147	109.7	125.1	-	90.6	147.3	110.6	125.6	-	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z320P5-525AXSP16	107.90	176.4	132.9	150.8	300.9	110.5	176.6	133.9	151.2	298.3	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z320P5-532AXSP16	99.60	164.7	123.6	140.7	283	102.1	165.1	124.6	141	280.7	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z320P5-625AXSP16	119.30	193.7	146.8	166.1	326.1	122.3	193.8	147.9	166.5	323.2	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z320P5-632AXSP16	111.60	186.6	138.2	157.1	312	114.5	183.8	139.3	157.6	309.1	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z320P7-425AXSP16	98.80	162.4	121.5	138.5	-	100.9	162.7	122.5	138.8	-	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z320P7-432AXSP16	90.10	149.7	111.6	127.5	-	92.4	150.1	112.7	127.9	-	146	22.5	2"	117	17.5	1-1/2"	176	31.5	2"
EAW-VD9104Z320P7-525AXSP16	110.00	179.5	135	153.3	-	112.5	180	136.1	153.8	-	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z320P7-532AXSP16	101.50	167.9	125.8	143	288.7	103.9	168.1	126.9	143.7	286	180	23.6	2"	144	15.6	2"	216	33.1	2"
EAW-VD9104Z320P7-625AXSP16	121.40	197.1	149.3	169	332	124.4	197.3	150.5	169.4	329.1	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z320P7-632AXSP16	113.50	187	140.7	159.9	318	116.7	187.3	141.9	160.3	314.8	225	25.4	2"	180	16.8	2"	270	29.8	3"
EAW-VD9104Z177F7-425AXSP16	87.60	142	107.2	121.6	241.8	89.1	142	107.7	121.4	239.1	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z177F7-432AXSP16	80.50	132.1	99.4	112.8	226.3	82.1	132.1	99.9	112.9	223.9	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z177F7-525AXSP16	96.50	155.5	118	133.4	261.6	98.3	155.2	118.5	133.3	258.5	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z177F7-532AXSP16	89.80	146.7	110.6	125.5	248.8	91.7	146.6	111.1	125.6	245.9	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z177F7-625AXSP16	105.40	168.8	128.4	145	279.7	107.6	168.3	128.8	144.9	276.5	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z177F7-632AXSP16	99.60	161.8	122.2	138.6	270.7	101.8	161.3	122.7	138.4	267.4	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z24716-425AXSP16	95.90	155.4	117	132.7	-	97.5	155.1	117.6	132.7	-	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z24716-432AXSP16	87.90	144	108.1	122.9	-	89.5	144	108.6	122.9	-	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z24716-525AXSP16	105.80	170.3	129	146	287.3	107.8	170.2	129.7	145.9	284.2	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z24716-532AXSP16	98.30	160.5	121	137.2	272.7	100.3	160.3	121.7	137.3	269.8	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z24716-625AXSP16	116.10	185.4	141.2	159.4	308.6	118.3	185	141.8	159.3	304.9	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z24716-632AXSP16	109.40	177.1	134.1	151.9	297.5	111.6	176.8	134.7	152	294.2	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z320P5-425AXSP16	104.30	169.1	127.3	144.3	-	105.8	169	127.7	144.3	-	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z320P5-432AXSP16	95.40	156.1	117	132.9	-	97	155.8	117.5	133.1	-	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z320P5-525AXSP16	116.40	187.1	141.7	160.3	-	118.4	186.9	142.2	160.1	-	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z320P5-532AXSP16	107.40	174.9	131.8	149.4	298.4	109.5	174.7	132.3	149.6	295.1	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z320P5-625AXSP16	128.80	205.4	156.4	176.5	343.3	131	204.9	157	176.3	339.2	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z320P5-632AXSP16	120.50	194.9	147.6	166.9	328.5	122.8	194.5	148.2	166.9	324.6	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z320P7-425AXSP16	106.20	172.4	129.7	147.1	-	107.8	172.2	130.4	147.2	-	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z320P7-432AXSP16	97.30	159.1	119.2	135.6	-	98.9	158.9	119.8	135.7	-	146	24.2	2"	117	18.7	1-1/2"	176	34	2"
EAW-VD9104Z320P7-525AXSP16	118.80	190.9	144.2	163.2	-	120.7	190.5	144.8	163.4	-	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z320P7-532AXSP16	109.60	178.3	134.2	152.3	-	111.5	178.2	134.9	152.5	-	180	25.4	2"	144	16.7	2"	216	35.6	2"
EAW-VD9104Z320P7-625AXSP16	131.40	209.5	159.4	179.9	350.2	133.6	209	159.9	179.5	346.2	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9104Z320P7-632AXSP16	123.00	198.6	150.5	170.2	334.9	125.2	198.3	151.1	170.2	331.4	225	27.2	2"	180	17.9	2"	270	32.3	3"
EAW-VD9106PA177F7-425AXSP12	108.20	175.6	132.1	149.8	-	110.2	175.9	133	150.4	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD9106PA177F7-432AXSP12	100.10	163.5	122.6	139.5	-	102.1	163.9	123.6	139.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD9106PA177F7-525AXSP12	119.00	190.8	144.3	163.2	-	121.2	191.1	145.4	164	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD9106PA177F7-532AXSP12	111.40	180.7	136.1	154.4	-	113.6	181.2	137.1	155	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD9106PA177F7-625AXSP12	129.10	205.6	156.7	176.5	342.9	131.9	206	157.8	177.1	340.4	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD9106PA177F7-632AXSP12	130.00	203.2	155.5	174.8	-	131.2	202.7	155.6	174.6	-	169	31	2"	135	23.7	1-1/2"	203	43.5	2"
EAW-VD9106PA24716-425AXSP12	117.00	190.2	142.8	162.2	-	119.1	190.7	144.1	162.9	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD9106PA24716-432AXSP12	108.00	176.7	132.3	150.6	-	110	177.4	133.5	151.2	-	146	23.2	2"	117	17.8	1-1/2"	176	32.6	2"
EAW-VD9106PA24716-525AXSP12	128.90	207.5	156.6	177.4	-	131.5	208	157.9	178.1	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD9106PA24716-532AXSP12	120.70	195.6	147.3	167	-	122.9	196.3	148.5	167.6	-	180	24.3	2"	144	16	2"	216	34.1	2"
EAW-VD9106PA24716-625AXSP12	141.20	224.6	170.9	192.8	376	144	224.9	172	193.3	373.4	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD9106PA24716-632AXSP12	134.00	215.6	163.2	184.5	364.3	136.7	216.2	164.4	185.3	361.6	225	26	2"	180	17.1	2"	270	31	3"
EAW-VD9106PA320P5-425AXSP08	114.70	200.9	147.9	170.2	354.3	120.7	203.2	151.1	172.6	353.2	225	19	2"	180	12.5	2"	270	21.1	3"</

EAW-VD91062A177F7-532AXSP16	136.60	215.5	164	184.7	-	137.5	214.2	163.6	184.1	-	180	31.6	2"	144	20.8	2"	216	44.3	2"
EAW-VD91062A177F7-625AXSP16	160.40	247.1	190.2	213.1	-	161	245.3	189.8	211.8	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD91062A177F7-632AXSP16	152.20	237	181.8	204	-	153.1	235.6	181.4	202.8	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD91062A24716-425AXSP12	140.10	226.5	170.6	193.5	-	142.5	226.4	171.6	193.7	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD91062A24716-432AXSP12	129.00	210.8	158.2	179.9	-	131.4	210.5	159.1	180	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD91062A24716-525AXSP12	153.90	246.9	187	211.6	-	156.7	246.7	187.9	211.7	412.6	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD91062A24716-532AXSP12	143.30	232.8	175.7	199	395.8	146.1	232.8	176.6	199.4	392.1	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD91062A24716-625AXSP12	166.80	265.7	202.7	228.2	442.7	170.1	265.6	203.7	228.5	438.5	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD91062A24716-632AXSP16	166.00	259.1	198.2	222.7	-	166.9	257.8	197.9	221.9	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD91062A320P5-425AXSP12	152.60	247.4	186.2	211.6	-	155.2	247.5	187.2	211.7	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD91062A320P5-432AXSP12	140.00	228.3	171.4	195	-	142.2	228.5	172.3	195.2	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD91062A320P5-525AXSP12	169.70	272.1	205.9	233	-	172.2	271.7	206.9	233.1	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD91062A320P5-532AXSP12	157.20	254.7	191.8	217.5	-	159.7	254.7	192.7	217.9	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD91062A320P5-625AXSP12	185.90	295.3	224.9	253.5	494.6	188.9	295	225.8	253.7	488.9	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD91062A320P5-632AXSP16	182.40	285.6	218.1	245.4	-	183.4	284.1	217.7	244.4	-	225	33.4	2"	180	22	2"	270	40.9	3"
EAW-VD91062A320P7-425AXSP12	155.50	251.9	189.7	215.2	-	157.9	252.2	190.6	215.5	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD91062A320P7-432AXSP12	142.50	233	174.6	198.5	-	144.9	232.9	175.7	198.9	-	203	25.4	2"	162	16.7	2"	244	30.8	3"
EAW-VD91062A320P7-525AXSP12	172.40	277.2	209.6	237.3	-	175.4	277	210.5	237.1	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD91062A320P7-532AXSP12	160.00	259.2	195.3	221.6	-	162.7	259.3	196.4	221.8	-	248	22.3	3"	198	18	2"	298	31.3	3"
EAW-VD91062A320P7-625AXSP12	189.00	300.5	228.7	257.9	503.6	192.2	300.3	229.8	258.1	497.9	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD91062A320P7-632AXSP12	177.10	285.5	216.4	244.5	482.1	180.5	285.1	217.3	244.5	477.2	304	22.9	3"	244	15.2	3"	365	32.2	3"
EAW-VD91062J177F7-425AXSP12	137.80	219.8	166.8	188.2	-	139.3	219	166.9	187.8	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J177F7-432AXSP12	127.10	204.7	154.6	175.2	-	128.8	204.3	155	174.8	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J177F7-525AXSP12	151.10	239.2	182.3	205.4	399.4	152.9	238.3	182.6	204.9	394.6	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J177F7-532AXSP12	141.10	226.1	171.6	193.8	380.3	142.9	225.1	171.9	193.2	375.9	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J177F7-625AXSP12	163.50	256.8	196.9	221.2	423.5	165.7	255.6	196.9	220.5	417.6	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD91062J177F7-632AXSP16	162.20	250.2	192.7	215.7	-	162.6	248.4	191.6	214.1	-	225	36.1	2"	180	23.8	2"	270	44.7	3"
EAW-VD91062J24716-425AXSP12	150.40	240.3	182	205.7	-	151.9	239.7	182.3	205.5	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J24716-432AXSP12	138.60	223.5	168.4	190.8	-	140.3	222.9	168.8	190.6	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J24716-525AXSP12	165.60	262.1	199.5	225	-	167.6	261.1	199.8	224.5	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J24716-532AXSP12	154.40	247.2	187.3	211.7	-	156.4	246.4	187.8	211.4	412.7	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J24716-625AXSP12	180.00	282.1	216.4	243	466.8	182.1	281.1	216.3	242.1	461	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD91062J24716-632AXSP12	169.80	270.1	205.9	232	450.8	172.2	268.9	206	231.2	445.2	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD91062J320P5-425AXSP12	163.10	261.8	197.8	224	-	165.2	261.1	198.2	223.8	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J320P5-432AXSP12	149.90	242.1	182.4	206.9	-	151.5	241.4	182.7	206.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J320P5-525AXSP12	181.70	288.3	218.9	247.3	-	183.6	287	219.2	246.6	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J320P5-532AXSP12	168.40	269.7	204.2	230.8	-	170.3	268.8	204.5	230.4	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J320P5-625AXSP12	199.50	313.1	239.4	269.3	-	201.5	311.3	239.3	268.1	-	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD91062J320P5-632AXSP12	187.20	297	226	254.9	497.8	189.3	295.9	226.1	254	491.2	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD91062J320P7-425AXSP08	148.30	254.6	188.5	216.2	442.3	154.4	256.1	191.2	218	439.2	304	17.2	3"	244	11.4	3"	365	24.2	3"
EAW-VD91062J320P7-432AXSP12	152.80	246.9	185.8	210.9	-	154.6	246.3	186.3	210.4	-	203	27.3	2"	162	18	2"	244	33.6	3"
EAW-VD91062J320P7-525AXSP12	184.90	293.7	223.3	251.9	-	187	292.6	223.3	251.3	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J320P7-532AXSP12	171.80	275	208.1	235.3	-	173.6	274.3	208.5	235	-	248	24.3	3"	198	19.4	2"	298	34.1	3"
EAW-VD91062J320P7-625AXSP12	203.20	318.8	243.7	274.1	-	205.5	317.6	244	273.4	-	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD91062J320P7-632AXSP12	190.90	302.6	230.4	259.6	507.6	193.1	301.6	230.6	259.2	501.7	304	24.9	3"	244	16.5	3"	365	35	3"
EAW-VD9108PA177F7-425AXSP08	142.30	233.7	175.1	199.4	-	146	234.9	177.3	200.8	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD9108PA177F7-432AXSP08	131.20	184.4	162.9	185.8	-	134.8	219.3	164.8	187	375.7	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD9108PA177F7-525AXSP08	156.40	255.9	193	219	435.1	160.8	257.1	195.1	220.3	432.4	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD9108PA177F7-532AXSP08	146.50	242.9	182.2	207.3	416	150.9	243.9	184.1	208.5	413.5	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD9108PA177F7-625AXSP12	181.10	280.3	215.6	241.6	-	182.8	279.6	215.7	241.3	-	225	32	2"	180	21.1	2"	270	39.4	3"
EAW-VD9108PA177F7-632AXSP08	157.70	260.3	195.5	222.7	441.5	162.7	261.7	197.8	223.9	438.7	338	20.2	3"	270	13.3	3"	406	28.3	3"
EAW-VD9108PA24716-425AXSP08	154.30	253.5	189.6	215.8	-	158	254.7	191.8	217.2	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD9108PA24716-432AXSP08	142.10	235.6	175.8	200.5	-	145.8	237	178	202	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD9108PA24716-525AXSP08	170.60	278.4	209.9	238.1	-	175.3	279.8	212	239.4	-	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD9108PA24716-532AXSP08	159.30	263	197.5	224.3	452.3	163.9	264.4	199.5	225.9	449.2	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD9108PA24716-625AXSP08	181.50	295	223.4	252.6	496.9	186.8	296.3	226	254.4	494.3	338	20.2	3"	270	13.3	3"	406	28.3	3"
EAW-VD9108PA24716-632AXSP08	171.80	283.2	213	242.2	481.9	177.2	284.4	215.3	243.7	478.3	338	20.2	3"	270	13.3	3"	406	28.3	3"
EAW-VD9108PA320P5-425AXSP08	169.00	278.8	208.1	237.1	-	173.1	280	210.5	238.6	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD9108PA320P5-432AXSP08	155.10	257.3	191.7	218.9	-	158.8	258.7	193.9	220.3	-	225	22.9	2"	180	15.1	2"	270	26.7	3"
EAW-VD9108PA320P5-525AXSP08	189.60	309	232.3	263.6	-	194.1	310.3	234.8	265.6	-	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD9108PA320P5-532AXSP08	175.80	289.9	216.9	246.9	-	180.4	291.3	219.2	248.7	-	282	19.5	3"	225	16.8	2"	338	27.4	3"
EAW-VD9108PA320P5-625AXSP08	203.40	329.8	249.5	282.5	558.3	209	331.3	252.1	284.3	555.3	338	20.2	3"	270	13.3	3"	406	28.3	3"
EAW-VD9108PA320P5-632AXSP08	191.00	314	236.3	268.2	535.9	196.5	315.5	238.6	269.6	532.6	338	20.2	3"	270	13.3	3"	406	28.3	3"
EAW-VD9108PA320P7-425AXSP08	171.40	283	211.3	240.8	-	175.5	284.3	213.5	242.1	-	225	22.9	2"						

EAW-VD91082A24716-525AXSP08	197.80	324.4	244.5	277.3	550.4	203.1	324.7	246.6	278.5	545.8	372	20.7	3"	298	13.7	3"	446	29.1	3"
EAW-VD91082A24716-532AXSP12	201.60	317.8	241.8	272.9	-	202.9	316.7	242	272	-	248	28.3	3"	198	22	2"	298	39.7	3"
EAW-VD91082A24716-625AXSP12	234.70	362.6	278.9	312.3	-	236	360.9	278.4	311.2	-	304	28.9	3"	244	19.1	3"	365	40.6	3"
EAW-VD91082A24716-632AXSP12	222.40	347.3	265.8	298.6	-	223.9	345.2	265.5	297.1	-	304	28.9	3"	244	19.1	3"	365	40.6	3"
EAW-VD91082A320P5-425AXSP08	197.70	324.8	243.5	276.9	-	202.1	325.6	245.5	277.7	-	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD91082A320P5-432AXSP08	180.40	299.8	223.9	255.2	-	184.7	300.7	225.8	256.2	-	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD91082A320P5-525AXSP08	218.70	357.3	269	305.1	609.3	223.8	358	271.4	306.4	603.1	372	20.7	3"	298	13.7	3"	446	29.1	3"
EAW-VD91082A320P5-532AXSP08	201.90	334.5	250.9	284.9	573.7	206.9	334.6	252.8	286.1	568.9	372	20.7	3"	298	13.7	3"	446	29.1	3"
EAW-VD91082A320P5-625AXSP08	237.30	385.8	292.2	330.8	650.5	243.5	386.6	294.6	331.6	644	451	22	3"	361	14.5	3"	541	27.1	4"
EAW-VD91082A320P5-632AXSP12	244.40	383	292.6	329.1	-	245.7	381	292.1	327.3	-	304	28.9	3"	244	19.1	3"	365	40.6	3"
EAW-VD91082A320P7-425AXSP08	201.50	330.6	247.5	282.2	-	205.8	331.7	249.8	283.3	-	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD91082A320P7-432AXSP08	183.70	305.4	228	260	-	188.4	306.5	230.1	261.1	-	304	19.9	3"	244	13.1	3"	365	27.9	3"
EAW-VD91082A320P7-525AXSP08	222.50	364	273.8	310.7	620.3	227.9	364.4	276	311.7	615.1	372	20.7	3"	298	13.7	3"	446	29.1	3"
EAW-VD91082A320P7-532AXSP08	205.70	340.3	255.1	290.2	584.3	210.8	341.2	257.6	291.6	579.7	372	20.7	3"	298	13.7	3"	446	29.1	3"
EAW-VD91082A320P7-625AXSP08	241.60	392.5	297.1	336.4	662.3	247.7	393	299.7	337.4	655.8	451	22	3"	361	14.5	3"	541	27.1	4"
EAW-VD91082A320P7-632AXSP08	225.80	372.2	280	318.3	633.4	232.3	373	282.4	319.6	627.1	451	22	3"	361	14.5	3"	541	27.1	4"
EAW-VD91082J177F7-425AXSP08	178.10	288.9	218.2	247.3	491.1	181.5	288.9	219.2	247.2	485.6	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J177F7-432AXSP08	163.90	269.3	202.6	228.8	461	167.1	269.2	203.6	230.2	456	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J177F7-525AXSP08	195.30	314.6	238.7	269.9	528.5	198.8	313.9	239.5	269.8	522.3	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J177F7-532AXSP08	181.80	297.4	223.9	254.2	503.7	185.7	296.7	225.1	254.4	497.9	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J177F7-625AXSP12	228.60	349.2	270	301.6	-	229.1	346.2	268.8	299.3	-	304	31.6	3"	244	20.9	3"	365	44.3	3"
EAW-VD91082J177F7-632AXSP12	217.30	335.4	258	289.2	-	217.7	332.4	256.9	287	-	304	31.6	3"	244	20.9	3"	365	44.3	3"
EAW-VD91082J24716-425AXSP08	195.30	315.8	238.4	270.1	-	198.6	315.6	239.3	270.4	-	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J24716-432AXSP08	179.10	293.3	220.6	250.6	503.5	182.6	293.6	221.6	250.9	498.0	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J24716-525AXSP08	214.20	344.6	261.4	295.5	581.3	218.1	344.3	262.3	295.4	575.1	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J24716-532AXSP08	199.20	325	245.4	278.1	552.3	203.1	324.6	246.6	278.2	546.4	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J24716-625AXSP08	230.80	369.4	281.2	317.5	615.1	235.6	368.7	282.5	317.2	608.3	451	23.7	3"	361	15.7	3"	541	29.6	4"
EAW-VD91082J24716-632AXSP12	237.30	367.6	282.4	316.5	-	238.1	368.8	281.2	314.5	-	304	31.6	3"	244	20.9	3"	365	44.3	3"
EAW-VD91082J320P5-425AXSP08	212.40	344.5	259.4	293.9	-	215.7	344.2	260.5	294.3	-	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J320P5-432AXSP08	194.40	318	238.7	271.1	-	197.9	317.9	239.9	271.5	-	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J320P5-525AXSP08	235.70	379.3	286.7	324.7	-	239.6	378.3	288.1	324.3	-	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J320P5-532AXSP08	217.80	354.4	267.5	303.1	603.7	221.8	353.9	268.4	303.2	597.8	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J320P5-625AXSP08	256.30	409.3	311.9	351.5	684.9	260.9	408.7	312.7	351.1	676.8	451	23.7	3"	361	15.7	3"	541	29.6	4"
EAW-VD91082J320P5-632AXSP08	239.80	388.1	294.2	332.7	654.4	244.4	387.4	295	332.2	647.5	451	23.7	3"	361	15.7	3"	541	29.6	4"
EAW-VD91082J320P7-425AXSP08	216.50	351.4	264.4	300.2	-	219.9	350.8	265.7	300.2	-	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J320P7-432AXSP08	198.40	324.4	243.2	276.9	-	202	324.3	244.5	276.8	-	304	21.6	3"	244	14.3	3"	365	30.4	3"
EAW-VD91082J320P7-525AXSP08	240.70	386.4	292.3	330.6	-	244.4	385.6	293.5	330.9	-	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J320P7-532AXSP08	222.20	361.3	272.5	308.9	616.1	226.4	361.1	273.6	309.2	609.6	372	22.5	3"	298	14.9	3"	446	31.6	3"
EAW-VD91082J320P7-625AXSP08	261.50	417.2	317.8	358.3	698.6	265.9	416.4	318.8	358.1	689.9	451	23.7	3"	361	15.7	3"	541	29.6	4"
EAW-VD91082J320P7-632AXSP08	244.80	395.4	300	338.8	668	249.3	394.9	300.9	338.9	660.3	451	23.7	3"	361	15.7	3"	541	29.6	4"
EAW-VD9110PA177F7-425AXSP08	185.90	299.2	225.7	255.7	-	188.7	299.5	227	256.4	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD9110PA177F7-432AXSP08	172.30	279.2	210	238.3	-	175	279.2	211.1	238.8	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD9110PA177F7-525AXSP08	206.30	327.1	248.5	280.7	-	209.2	327.4	249.8	281	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD9110PA177F7-532AXSP08	194.00	310.6	234.8	265.9	-	196.9	310.7	236.3	266.4	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD9110PA177F7-625AXSP08	219.70	345	263.8	296.6	-	223	345.1	265.2	297.1	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA177F7-632AXSP08	209.40	322.5	253.2	285.3	557.7	212.9	322.7	254.3	285.8	553.3	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA24716-425AXSP06	185.40	308.4	229.9	262.6	-	191.1	310.6	233.2	264.5	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD9110PA24716-432AXSP08	186.00	301.5	226.7	257.3	-	188.8	302	228	257.9	-	225	26.9	2"	180	17.7	2"	270	32.2	3"
EAW-VD9110PA24716-525AXSP08	223.80	356	270	304.9	-	226.9	356	271.6	305.4	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD9110PA24716-532AXSP08	209.80	336.6	254.4	288	-	212.8	337	255.8	288.3	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD9110PA24716-625AXSP08	239.50	376.9	287.4	323.6	-	243	376.8	289.2	324.4	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA24716-632AXSP08	227.60	361.9	274.8	310.5	-	231.3	361.8	276.2	310.8	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA320P5-425AXSP06	203.80	338.7	252.2	288.1	-	209.4	341.1	255.6	290.7	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD9110PA320P5-432AXSP06	186.30	312.6	232	265.4	-	191.8	314.6	235.2	267.7	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD9110PA320P5-525AXSP06	230.20	380.1	284.6	323.8	-	237.3	382.4	288.3	326.4	-	372	19.1	3"	298	12.6	3"	446	26.8	3"
EAW-VD9110PA320P5-532AXSP08	230.30	370.7	279.8	316.8	-	233.6	371.1	280.9	317.1	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD9110PA320P5-625AXSP08	266.80	421.7	320.8	361.7	-	270.5	421.7	322.5	362.2	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA320P5-632AXSP08	251.40	401.1	304.1	343.7	-	255.3	401.7	305.9	344.2	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA320P7-425AXSP06	206.70	343.7	256	292.5	-	212.5	346.3	259.5	294.8	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD9110PA320P7-432AXSP06	189.10	317.1	235.4	269.4	-	194.9	319.3	238.6	271.6	-	293	18.1	3"	234	16.2	2"	352	25.4	3"
EAW-VD9110PA320P7-525AXSP06	233.80	385.8	288.6	329.1	-	240.6	388.1	292.4	331.2	-	372	19.1	3"	298	12.6	3"	446	26.8	3"
EAW-VD9110PA320P7-532AXSP08	233.30	376	283.6	321.2	-	236.9	376.7	285.5	322.4	-	282	23.5	3"	225	19.5	2"	338	33	3"
EAW-VD9110PA320P7-625AXSP08	271.00	428.6	325.9	367.5	-	274.6	428.3	327.9	368.3	-	338	24.2	3"	270	16	3"	406	33.9	3"
EAW-VD9110PA320P7-632AXSP08	255.40	407.1	308.5	348.7	-	258.9	407.7	310.3	349.3										

EAW-VD9110ZA320P5-432AXSP08	236.80	383.4	288.4	327.3	-	239.6	383	289.3	327.3	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD9110ZA320P5-525AXSP08	286.90	456.9	346.7	391.4	-	290.5	455.6	347.1	390.9	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD9110ZA320P5-525AXSP08	266.60	427.2	323.1	365.7	-	269.7	426.5	324.1	365.1	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD9110ZA320P5-625AXSP08	313.20	492.9	376.4	423.8	-	317.2	491.7	377	422.8	-	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD9110ZA320P5-632AXSP08	294.50	467.8	355.4	400.8	-	297.9	466.2	356.2	400.1	-	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD9110ZA320P7-425AXSP06	245.80	408.9	305.3	348.1	-	252.6	410.4	308.7	350.2	-	406	19.7	3"	325	13	3"	487	27.7	3"
EAW-VD9110ZA320P7-432AXSP08	241.10	390.6	293.8	333.5	-	244.2	390.4	294.9	333.5	-	304	23.8	3"	244	15.8	3"	365	33.5	3"
EAW-VD9110ZA320P7-525AXSP08	292.00	464.8	353	398.6	-	295.4	463.7	353.6	397.7	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD9110ZA320P7-532AXSP08	270.90	434.8	328.5	372	-	274.2	434.2	329.7	372.2	-	372	24.7	3"	298	16.3	3"	446	34.7	3"
EAW-VD9110ZA320P7-625AXSP08	318.50	501.6	382.9	431.1	-	322.2	500.6	383.6	430.2	-	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD9110ZA320P7-632AXSP08	299.70	475.8	361.8	408.1	-	303.3	474.5	362.2	407.6	-	451	26	3"	361	17.1	3"	541	32.7	4"
EAW-VD9110Z117F7-425AXSP08	232.60	368.5	280.3	316.3	-	234.5	366.6	280	314.6	-	304	26.1	3"	244	17.2	3"	365	36.6	3"
EAW-VD9110Z117F7-432AXSP08	215.20	343.5	260.1	294.1	-	217.2	342.2	260.2	292.9	-	304	26.1	3"	244	17.2	3"	365	36.6	3"
EAW-VD9110Z117F7-525AXSP08	256.20	400.9	306.7	344.9	-	257.9	398.8	306.2	343	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z117F7-532AXSP08	239.70	379.1	288.4	325	-	241.4	376.9	288.3	324	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z117F7-625AXSP08	276.30	428.5	329.5	369.2	704.2	278.4	425.5	329	367.5	694.4	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z117F7-632AXSP08	261.60	410.4	314.2	353.1	681.7	263.9	408	313.9	351.5	671.8	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z24716-425AXSP08	253.50	403.1	306	345.2	-	255.5	401.4	306	344.3	-	304	26.1	3"	244	17.2	3"	365	36.6	3"
EAW-VD9110Z24716-432AXSP08	233.90	374.5	283.4	320.5	-	236.1	372.8	283.4	319.5	-	304	26.1	3"	244	17.2	3"	365	36.6	3"
EAW-VD9110Z24716-525AXSP08	279.60	439.4	335.6	377.3	-	281.9	437.7	335	376.4	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z24716-532AXSP08	261.60	414.5	314.8	355.2	-	263.5	412.5	315.1	354	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z24716-625AXSP08	303.50	470.8	361.6	405.6	-	305.6	467.9	361	403.5	-	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z24716-632AXSP08	286.60	449.5	343.7	386.6	748.6	289.2	447.5	343.4	385.4	739.3	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z320P5-425AXSP06	260.60	426.2	320	363.4	-	266.1	426	322.1	364	-	406	21.4	3"	325	14.1	3"	487	30	3"
EAW-VD9110Z320P5-434AXSP08	253.00	405.6	306.4	346.9	-	254.9	404.5	306.4	345.9	-	304	26.1	3"	244	17.2	3"	365	36.6	3"
EAW-VD9110Z320P5-525AXSP08	306.50	483.3	368.5	414.8	-	309	481	367.6	412.9	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z320P5-532AXSP08	284.40	452.3	342.8	387.4	-	286.5	450	343.1	386	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z320P5-625AXSP08	335.00	521.8	399.6	448.8	-	337.3	518.9	399.3	446.8	-	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z320P5-632AXSP08	314.60	495	377.2	424.9	-	317	491.8	376.8	423.4	-	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z320P7-425AXSP06	266.00	434.8	326.1	370.5	-	271.2	434.9	328.4	371.3	-	406	21.4	3"	325	14.1	3"	487	30	3"
EAW-VD9110Z320P7-432AXSP06	242.70	400.9	300.2	341.7	-	248.2	401.7	302.2	342.7	-	406	21.4	3"	325	14.1	3"	487	30	3"
EAW-VD9110Z320P7-525AXSP06	298.20	484.5	365.4	413.9	821.5	304.4	484.1	368	415	813.3	507	23.1	3"	406	15.2	3"	609	27.8	4"
EAW-VD9110Z320P7-532AXSP08	289.70	461.3	349.9	394.8	-	292.5	459.2	349.9	393.7	-	372	26.9	3"	298	17.8	3"	446	37.8	3"
EAW-VD9110Z320P7-625AXSP08	341.30	531.4	407.3	457.4	-	343.4	528.7	406.6	455.7	-	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9110Z320P7-632AXSP08	320.80	504.3	384.7	433.4	-	322.8	502	384.4	431.3	-	451	28.2	3"	361	18.6	3"	541	35.8	4"
EAW-VD9112PA117F7-425AXSP06	214.80	348.7	262.2	298	-	219	350	264.4	299.1	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD9112PA117F7-432AXSP06	198.80	325	243.6	277	-	202.6	325.9	245.6	278.2	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD9112PA117F7-525AXSP06	240.50	385.6	292	330.1	-	244.9	386.7	294.1	331.5	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA117F7-532AXSP06	224.90	365.6	275.8	312.6	-	229.8	366.4	277.7	313.8	618.5	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA117F7-625AXSP08	270.90	420	322.5	361.4	-	273.5	418.9	322.7	360.9	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD9112PA117F7-632AXSP08	258.70	405.2	309.6	348	-	261.2	404.2	309.9	347.6	-	338	28.2	3"	270	18.6	3"	406	39.5	3"
EAW-VD9112PA24716-425AXSP06	232.20	377.6	283.8	322.5	-	236.6	378.7	286	324	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD9112PA24716-432AXSP06	214.20	351.3	262.9	299.2	-	218.5	352.1	264.9	300.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD9112PA24716-525AXSP06	261.00	419.5	317	358.9	-	265.8	420.3	319.6	360.2	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA24716-532AXSP06	244.30	395.9	297.9	338.3	-	249.2	397.2	300.4	340	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA24716-625AXSP06	280.20	446.8	339.8	383.3	748.2	286.3	448	342.5	384.9	743.2	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD9112PA24716-632AXSP06	265.60	428.6	324.3	367.3	724.7	271.6	429.8	327.2	368.4	720.3	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD9112PA320P5-425AXSP04	226.00	397.1	292.2	336.5	702.7	238.1	402.5	299	341.7	700.5	451	16.7	3"	361	11	3"	541	19.9	4"
EAW-VD9112PA320P5-432AXSP06	233.30	383.2	286.5	326.2	-	237.6	384.1	288.6	327.7	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD9112PA320P5-525AXSP06	288.20	465	350.9	398	-	293.8	466.8	354	399	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA320P5-532AXSP06	268.20	436.4	328	372.5	-	273.3	437	330.1	373.7	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA320P5-625AXSP06	313.40	499.6	379	428.2	-	319	501.1	382.3	429.5	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD9112PA320P5-632AXSP06	295.20	475.4	359.3	406.4	-	301.1	476.2	362.2	408.4	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD9112PA320P7-425AXSP04	229.70	420.9	296.7	341.5	712.6	241.8	406.6	303.5	346.6	711.8	451	16.7	3"	361	11	3"	541	19.9	4"
EAW-VD9112PA320P7-432AXSP06	236.60	388.8	290.4	331.1	-	241.2	390	293	332.5	-	293	21.1	3"	234	18.2	2"	352	29.6	3"
EAW-VD9112PA320P7-525AXSP06	292.80	472	355.9	403.9	-	298	473.9	359.1	405.6	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA320P7-532AXSP06	272.20	442.6	332.4	377.6	-	277.4	443.6	335.4	379.1	-	372	22.1	3"	298	14.6	3"	446	31	3"
EAW-VD9112PA320P7-625AXSP06	318.30	507.8	384.9	435.1	-	324.3	509	388.1	436.8	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD9112PA320P7-632AXSP06	299.80	482.5	364.4	413	-	305.3	483.4	367.4	414.4	-	451	23.3	3"	361	15.3	3"	541	29.1	4"
EAW-VD9112PJ177F-425AXSP06	232.50	373.2	282.1	319	-	235.5	373	283.2	319.4	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD9112PJ177F-432AXSP06	214.70	347.6	261.6	296.8	-	217.7	347.3	262.7	297.1	-	293	23.1	3"	234	19.5	2"	352	32.4	3"
EAW-VD9112PJ177F-525AXSP06	260.80	413.6	314.5	354.6	-	264.1	413.4	315.7	355	-	372	24.1	3"	361	15.3	3"	446	33.8	3"
EAW-VD9112PJ177F-532AXSP06	244.60	391.7	296.5	335.6	-	248.2	391.7	297.8	335.5	-	372	24.1	3"	298	15.9	3"	446	33.8	3"
EAW-VD9112PJ177F-625AXSP06	279.80	439.8	336.2	377.9	729.7	283.8	439.2	327.4	377.9	722.4	451	25.3	3"	361	16.7	3"	541	31.9	4"
EAW-VD9112PJ177F-632AXSP06	265.90	422.7	321.8	363	708.2	270.3	422.9	323.2	363.1	701.6	451								

EAW-VD9112ZA320P7-425AXSP06	308.30	501.1	376.5	427.3	-	313.3	501	379	428	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD9112ZA320P7-432AXSP06	282.80	462.5	346.6	394.1	-	287.6	462.4	348.8	395.4	-	406	22.7	3"	325	15	3"	487	31.9	3"
EAW-VD9112ZA320P7-525AXSP06	347.30	557.8	422.1	477.6	-	353.2	557.3	423.7	478	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD9112ZA320P7-532AXSP06	321.90	522.6	393.5	446.4	-	327.8	521.9	395.6	446.6	-	507	24.4	3"	406	16.1	3"	609	29.6	4"
EAW-VD9112ZA320P7-625AXSP06	375.60	598.6	455.3	513.6	1002.2	382	597.5	456.9	513.4	992.2	609	21.8	4"	487	17.5	3"	730	30.6	4"
EAW-VD9112ZA320P7-632AXSP06	351.70	567.6	429.9	485.9	959.1	358.6	567.7	431.9	486.8	949.4	609	21.8	4"	487	17.5	3"	730	30.6	4"
EAW-VD9112ZJ177F7-425AXSP06	273.60	436.8	331.3	374.6	-	277.1	435.9	331.5	373.9	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ177F7-432AXSP06	252.20	407.4	307.5	348.5	-	255.7	405.9	308.3	347.8	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ177F7-525AXSP06	304.10	481.1	366.9	413.3	803.7	307.6	479.2	367.4	412.2	793.1	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ177F7-532AXSP06	283.70	454.9	345.5	390	765.8	287.7	453.5	346	388.8	756.8	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ177F7-625AXSP08	340.00	519.9	401.8	449.4	-	340.9	515.6	400.1	445.5	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD9112ZJ177F7-632AXSP08	323.00	499.1	383.7	429.7	-	323.7	494.8	381.6	427	-	451	32.6	3"	361	21.5	3"	541	42	4"
EAW-VD9112ZJ24716-425AXSP06	298.50	477.6	361.4	409.4	-	301.7	476.4	362.2	408.3	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ24716-432AXSP06	275.20	443.9	334.8	379.5	-	278.4	442.8	335.6	379.2	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ24716-525AXSP06	333.30	527.3	401.5	452.8	-	337.3	525.9	402	451.6	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ24716-532AXSP06	310.60	497.4	377.1	426.2	840.1	315.1	496.5	378.1	425.5	831	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ24716-625AXSP06	357.30	562.1	430.3	483.4	930.3	362.1	559.3	430.8	482.3	918.9	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD9112ZJ24716-632AXSP06	337.40	537.2	409.3	461.2	898.3	342.3	535.6	410.2	460.5	887.1	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD9112ZJ320P5-425AXSP06	324.40	521	393.5	445.6	-	327.9	518.8	394.3	444.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ320P5-432AXSP06	297.50	480.6	362.2	410.7	-	300.9	480.2	363.3	410.4	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ320P5-525AXSP06	365.30	579.9	440.7	497.8	-	369.6	578.1	441.2	496.2	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ320P5-532AXSP06	339.40	542.8	411.4	464.8	-	343.1	541.7	411.7	464	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ320P5-625AXSP06	396.50	622.9	476.1	535.5	-	400.7	620.3	476.5	534	-	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD9112ZJ320P5-632AXSP06	371.40	590.6	449.8	506.8	990.6	376.2	588.6	450.1	505.8	978.7	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD9112ZJ320P7-425AXSP06	330.50	531.6	401.1	454.4	-	334.3	529.7	402.2	453.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ320P7-432AXSP06	303.20	490.2	369.4	418.6	-	306.8	489.1	370.1	418.5	-	406	24.7	3"	325	16.3	3"	487	34.7	3"
EAW-VD9112ZJ320P7-525AXSP06	372.40	590.9	449.5	507	-	376.4	589.4	450.1	505.6	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ320P7-532AXSP06	345.60	553.5	419.1	473.8	-	349.8	552	419.8	473.2	-	507	26.4	3"	406	17.4	3"	609	32.4	4"
EAW-VD9112ZJ320P7-625AXSP06	404.00	635.1	485.2	545.8	-	408.5	632	485.2	543.9	-	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD9112ZJ320P7-632AXSP06	378.60	602.6	457.9	516.9	1011.2	383.6	599.9	458.4	515.3	998.2	609	23.8	4"	487	18.8	3"	730	33.4	4"
EAW-VD9114PA177F7-432AXSP04	234.60	398.4	296.5	338.7	692.9	244.1	402.1	301.5	342.7	689.2	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA177F7-432AXSP06	238.40	385.1	289.8	328.5	-	241.3	384.5	291.1	329.1	-	293	24.1	3"	234	20.2	2"	352	33.8	3"
EAW-VD9114PA177F7-525AXSP06	288.40	455.9	346.8	391.2	-	292	456.4	348.6	391.6	-	372	25.1	3"	298	16.5	3"	446	35.2	3"
EAW-VD9114PA177F7-532AXSP06	271.10	432.8	327.6	370.3	-	274.6	432.9	329.1	371	-	372	25.1	3"	298	16.5	3"	446	35.2	3"
EAW-VD9114PA177F7-625AXSP06	309.50	483.6	370.4	415.9	-	313.6	483.8	371.8	416.5	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PA177F7-632AXSP06	295.00	466.1	355.6	400.6	-	299.5	466.4	356.6	400.8	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PA24716-425AXSP04	255.20	431.8	320.8	366.9	752.1	264.9	435.6	326.5	371	748.7	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA24716-432AXSP04	234.00	401.4	297.4	340.9	703.3	243.5	405.2	302.3	344.3	700.4	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA24716-525AXSP06	312.80	496.1	376.8	425.5	-	316.5	496.3	378.4	426.2	-	372	25.1	3"	298	16.5	3"	446	35.2	3"
EAW-VD9114PA24716-532AXSP06	293.10	468.9	354.8	401.1	-	296.8	468.7	356.2	401.5	-	372	25.1	3"	298	16.5	3"	446	35.2	3"
EAW-VD9114PA24716-625AXSP06	336.80	528.4	403.6	454.3	-	341.2	528.3	405.5	454.8	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PA24716-632AXSP06	320.30	507.5	385.9	435.3	-	324.3	507.3	387.3	435.8	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PA320P5-425AXSP04	281.70	474.2	352.4	402.9	-	291.5	478.5	357.8	406.9	-	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA320P5-432AXSP04	256.70	438.2	324	371.6	-	266.2	441.8	329.3	375.2	-	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA320P5-525AXSP04	313.90	526.9	393.3	448.6	910.9	324.5	531.1	399.4	453.1	905.9	564	16.9	4"	451	13.7	3"	676	23.7	4"
EAW-VD9114PA320P5-532AXSP04	289.90	493.8	367	419.8	859	301.5	497.6	373.3	424	855.5	564	16.9	4"	451	13.7	3"	676	23.7	4"
EAW-VD9114PA320P5-625AXSP06	375.40	591.2	450.5	507.1	-	379.9	591.2	452.8	507.8	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PA320P5-632AXSP06	353.80	562.4	427.2	482	-	358.6	562.3	428.9	482.6	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PA320P7-425AXSP04	286.00	481.2	357.2	409.1	-	296.2	485.8	362.9	413.1	-	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA320P7-432AXSP04	260.50	444.4	328.7	377.1	-	270.5	448.5	334.4	381.1	-	451	18.7	3"	361	12.3	3"	541	22.7	4"
EAW-VD9114PA320P7-525AXSP04	318.70	534.7	398.8	455.1	925.2	330.5	539	405.8	459.7	920.1	564	16.9	4"	451	13.7	3"	676	23.7	4"
EAW-VD9114PA320P7-532AXSP04	294.40	500.8	372.2	425.5	872	306.2	505	378.5	430.1	869	564	16.9	4"	451	13.7	3"	676	23.7	4"
EAW-VD9114PA320P7-625AXSP04	342.20	572.2	428.4	488.3	979.5	355.3	577.3	436	493	973.7	676	17.7	4"	541	11.7	4"	812	24.9	4"
EAW-VD9114PA320P7-632AXSP06	358.80	570.8	433.3	489	-	363.8	570.8	435.1	489.7	-	451	26.2	3"	361	17.3	3"	541	33.3	4"
EAW-VD9114PJ177F7-425AXSP04	257.90	428.1	320.5	364.9	737.9	265.3	430.2	323.8	366.7	732.5	451	20.3	3"	361	13.4	3"	541	24.9	4"
EAW-VD9114PJ177F7-432AXSP04	237.00	398.8	297.3	339.2	691.4	244.3	400.8	300.9	341.2	686.8	451	20.3	3"	361	13.4	3"	541	24.9	4"
EAW-VD9114PJ177F7-525AXSP04	284.30	469.9	353.4	401.6	799.6	293.1	472.1	357.3	404.2	794.7	564	18.4	4"	451	14.7	3"	676	25.9	4"
EAW-VD9114PJ177F7-532AXSP06	292.30	462.8	352	396.8	-	295.2	461.2	352.1	395.9	-	372	27.4	3"	298	18.1	3"	446	38.4	3"
EAW-VD9114PJ177F7-625AXSP06	335.20	519.1	399	447	-	337.8	517.7	399.1	446.2	-	451	28.6	3"	361	18.8	3"	541	36.5	4"
EAW-VD9114PJ177F7-632AXSP06	319.30	499.4	381.9	429.2	-	321.8	498.1	382.3	428.6	-	451	28.6	3"	361	18.8	3"	541	36.5	4"
EAW-VD9114PJ24716-425AXSP04	280.80	464.7	347.7	395.8	-	288.6	466.8	351.2	398.4	-	451	20.3	3"	361	13.4	3"	541	24.9	4"
EAW-VD9114PJ24716-432AXSP04	257.50	431.9	321.4	367.2	750	265.2	433.9	325.2	369.7	745.8	451	20.3	3"	361	13.4	3"	541	24.9	4"
EAW-VD9114PJ24716-525AXSP04	310.80	512.2	385.2	437.6	874.5	319.8	514.3	389.3	440.1	868.5	564	18.4	4"	451	14.7	3"	676	25.9	4"
EAW-VD9114PJ24716-532AXSP04	289.10	483.2	361.7	412.2	831.4	298.7	485.8</												

EAW-VD91142A320P7-632AXSP06	424.60	672	510.6	575.8	-	428.9	669	511.9	575	-	609	24.8	4"	487	19.5	3"	730	34.8	4"
EAW-VD91142J177F-425AXSP06	326.80	516.7	393.1	442.8	-	328.9	514	392.6	441.1	-	406	28	3"	325	18.5	3"	487	39.3	3"
EAW-VD91142J177F-432AXSP06	302.40	481	364.8	412.5	-	304.6	479	364.3	410.8	-	406	28	3"	325	18.5	3"	487	39.3	3"
EAW-VD91142J177F-525AXSP06	364.30	568.2	435.1	489.1	-	366.5	565.1	434.3	486.4	-	507	29.8	3"	406	19.6	3"	609	37.1	4"
EAW-VD91142J177F-532AXSP06	341.30	537.8	409.8	461.4	-	343.6	534.5	408.8	459.2	-	507	29.8	3"	406	19.6	3"	609	37.1	4"
EAW-VD91142J177F-625AXSP06	391.20	603.6	465	520.2	990.4	393.5	599.3	463.7	517.8	976.5	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J177F-632AXSP06	370.70	579.2	443.8	498.5	959.1	373.3	575	442.7	495.5	945	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J24716-425AXSP04	324.50	540.2	404.3	460.4	928	333.4	541	408.6	462.1	919.8	609	18.8	4"	487	15.3	3"	730	26.5	4"
EAW-VD91142J24716-432AXSP06	328.80	524.3	397.6	449.5	-	331.2	522.8	396.8	447.3	-	406	28	3"	325	18.5	3"	487	39.3	3"
EAW-VD91142J24716-525AXSP06	397.80	622.9	476.4	535.4	-	400.9	619.5	475.5	533.1	-	507	29.8	3"	406	19.6	3"	609	37.1	4"
EAW-VD91142J24716-532AXSP06	372.80	587.4	447.4	504.5	-	375.2	584.5	447	502.7	-	507	29.8	3"	406	19.6	3"	609	37.1	4"
EAW-VD91142J24716-625AXSP06	429.20	663.3	509.8	571.6	-	431.5	659.1	508.8	568.6	-	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J24716-632AXSP06	406.30	634.6	485.5	545.2	-	408.6	630.8	485	543.4	-	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J320P5-425AXSP04	354.50	587.6	440.3	501.4	1014	363.8	589.6	444.3	503.3	1004.6	609	18.8	4"	487	15.5	3"	730	26.5	4"
EAW-VD91142J320P5-432AXSP04	322.90	543.2	404.7	462	942.3	332.3	544.3	408.4	464.2	933.1	609	18.8	4"	487	15.5	3"	730	26.5	4"
EAW-VD91142J320P5-525AXSP04	395.90	653.9	491.8	558.3	1114.4	406.6	654.3	495.3	559.6	1103.1	755	20.1	4"	604	13.2	4"	906	24.4	(2) 4"
EAW-VD91142J320P5-532AXSP06	405.50	641.3	487.5	550.6	-	408.2	637.9	486.9	547.5	-	507	29.8	3"	406	19.6	3"	609	37.1	4"
EAW-VD91142J320P5-625AXSP06	473.90	735.4	564.4	633.5	-	476.4	730.2	563	629.8	-	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J320P5-632AXSP06	445.50	697.9	533.1	599.3	-	448	693.4	532.3	597.1	-	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J320P7-425AXSP04	361.70	599.4	448.6	511.1	-	371.5	601.7	453	513.4	-	609	18.8	4"	487	15.3	3"	730	26.5	4"
EAW-VD91142J320P7-432AXSP04	329.30	553.8	412.6	471.2	960.3	338.7	555.2	416.6	473.2	952.8	609	18.8	4"	487	15.5	3"	730	26.5	4"
EAW-VD91142J320P7-525AXSP04	403.40	666.1	501.4	569.3	1136.2	414.6	666.9	505.2	571.1	1125.2	755	20.1	4"	604	13.2	4"	906	24.4	(2) 4"
EAW-VD91142J320P7-625AXSP06	413.10	654.1	496.8	561.3	-	416.2	651	496.6	558.5	-	507	29.8	3"	406	19.6	3"	609	37.1	4"
EAW-VD91142J320P7-625AXSP06	482.10	749.8	575.2	644.9	-	485	745	574.1	642.4	-	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD91142J320P7-632AXSP06	453.50	711.1	543.6	611.3	-	456.2	706.8	542.3	608.4	-	609	27.1	4"	487	21	3"	730	38.1	4"
EAW-VD9116PA177F-425AXSP04	281.10	463.4	346.8	395.2	-	288.6	465.9	350.6	397.4	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA177F-432AXSP04	258.70	431.7	322.4	367.5	749.3	266.2	433.8	325.8	370	744	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA177F-525AXSP04	309.40	507.3	382.2	433.8	864.5	318.4	510.4	387	436.6	858.1	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA177F-532AXSP04	289.30	481.1	360.3	410.2	826	298.5	483.9	365	413.4	821.1	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA177F-625AXSP06	360.10	558.5	428.8	481.2	-	363.6	557.1	429.7	479.9	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD9116PA177F-632AXSP06	343.90	538.8	411.5	462.6	-	347.2	537.5	412.6	462.1	-	451	29.2	3"	361	19.3	3"	541	37.5	4"
EAW-VD9116PA24716-425AXSP04	304.90	501.7	375.4	427.5	-	312.5	505	379.8	430.4	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA24716-432AXSP04	280.40	466.7	347.7	396.8	-	288.3	469.4	352.1	399.8	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA24716-525AXSP04	337.40	552.4	415.4	471.5	-	346.4	554.6	420.4	474.9	936.6	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA24716-532AXSP04	314.30	521.6	390.5	444.5	896.4	323.9	524.4	395.4	447.8	891.7	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA24716-625AXSP04	359.30	585.2	442.7	501.4	987.7	370.1	588.5	447.9	504.4	982.5	676	19.7	4"	541	13	4"	812	27.7	4"
EAW-VD9116PA24716-632AXSP04	339.80	561.2	421.7	479.6	955.9	350.5	563.9	427.1	482.8	950.2	676	19.7	4"	541	13	4"	812	27.7	4"
EAW-VD9116PA320P5-425AXSP04	334.20	551.3	411.9	469.5	-	342.1	555	416.7	472.5	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA320P5-432AXSP04	306.30	509.3	378.9	433	-	314.2	512.2	383.4	435.9	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA320P5-525AXSP04	374.90	612.1	459.5	522.6	-	384	615.7	464.6	525.8	-	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA320P5-532AXSP04	347.40	573.6	429.3	489.1	-	356.7	576.6	434.2	491.8	-	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA320P5-625AXSP04	402.70	653.9	494.1	559.8	1109.5	413.8	658	499.5	563.4	1103.6	676	19.7	4"	541	13	4"	812	27.7	4"
EAW-VD9116PA320P5-632AXSP04	377.70	622	467.5	531.1	1064.3	388.7	625.3	473.2	534.9	1057.9	676	19.7	4"	541	13	4"	812	27.7	4"
EAW-VD9116PA320P7-425AXSP04	339.00	559.5	418.1	476.7	-	347.2	562.5	422.7	479.5	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA320P7-432AXSP04	311.00	516.7	384.4	439.5	-	318.5	519.5	389.4	442.3	-	451	20.7	3"	361	13.6	3"	541	25.5	4"
EAW-VD9116PA320P7-525AXSP04	380.80	621.3	466.9	530.2	-	390	624.9	472.1	533.5	-	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA320P7-532AXSP04	352.60	581.8	435.5	495.9	-	362	585.3	440.4	499.9	-	564	18.9	4"	451	15	3"	676	26.5	4"
EAW-VD9116PA320P7-625AXSP04	409.50	664.5	501.8	568.7	1128.2	420.6	668.3	507.8	572.1	1121.5	676	19.7	4"	541	13	4"	812	27.7	4"
EAW-VD9116PA320P7-632AXSP04	383.60	631.2	474.9	539.6	1080.8	394.8	634.7	479.9	542.7	1074.4	676	19.7	4"	541	13	4"	812	27.7	4"
EAW-VD9116PJ177F-425AXSP04	305.80	496.8	373.3	423.8	-	311.5	497.3	376.3	425.1	-	451	22.5	3"	361	14.8	3"	541	28	4"
EAW-VD9116PJ177F-432AXSP04	282.20	462.6	346.6	394.2	-	287.9	463.1	349.5	395.3	-	451	22.5	3"	361	14.8	3"	541	28	4"
EAW-VD9116PJ177F-525AXSP04	338.40	545	412.7	467	921.1	345.3	545.7	415.6	468.3	913	564	20.7	4"	451	16.2	3"	676	29	4"
EAW-VD9116PJ177F-532AXSP04	316.50	516.5	389	441.4	880	323.8	517.4	392.2	442.9	871.7	564	20.7	4"	451	16.2	3"	676	29	4"
EAW-VD9116PJ177F-625AXSP04	360.20	577.3	439.2	495.5	963.7	368	578.2	442.3	497	955.3	676	19.7	4"	541	14.2	4"	812	30.2	4"
EAW-VD9116PJ177F-632AXSP04	341.70	554.9	419.7	475.2	935.8	350.1	555.3	423.1	477.1	927.2	676	21.5	4"	541	14.2	4"	812	30.2	4"
EAW-VD9116PJ24716-425AXSP04	331.20	538.6	405.2	460	-	337.4	540.8	408.3	462	-	451	22.5	3"	361	14.8	3"	541	28	4"
EAW-VD9116PJ24716-432AXSP04	305.60	500.4	375.1	426.7	-	311.7	501.6	378.1	428.6	-	451	22.5	3"	361	14.8	3"	541	28	4"
EAW-VD9116PJ24716-525AXSP04	369.00	593.5	448.5	508.3	-	376.4	594.8	452.2	509.4	-	564	20.7	4"	451	16.2	3"	676	29	4"
EAW-VD9116PJ24716-532AXSP04	344.50	560.6	422	478.7	-	352	561.6	425.6	480.5	-	564	20.7	4"	451	16.2	3"	676	29	4"
EAW-VD9116PJ24716-625AXSP04	394.30	631	479.5	541.5	1057.3	402.8	631.5	483.1	542.8	1048.4	676	21.5	4"	541	14.2	4"	812	30.2	4"
EAW-VD9116PJ24716-632AXSP04	372.70	603.4	457.1	517.5	1020.8	381.2	605.3	460.6	519.1	1013.5	676	21.5	4"	541	14.2	4"	812	30.2	4"
EAW-VD9116PJ320P5-425AXSP04	362.30	590.9	443.4	504.2	-	368.8	592.3	446.6	505.4	-	451	22.5	3"	361	14.8	3"	541	28	4"
EAW-VD9116PJ320P5-432AXSP04	331.90	545.4	407.7	464.4	-	338.5	547	411.1	466	-	451	22.5	3"	361	14.8	3"	541	28	4"
EAW-VD9116PJ320P5-525AXSP04	407.10	657	495.9	562.1	-	414.7	658.3	499.2	564.2	-	564	20.7	4"	451	16.2</				

EAW-VD9116Z177F7-625AXSP06	455.20	695.8	537.9	600.8	-	455.8	689.9	534.8	596.3	-	609	30.4	4"	487	23.2	3"	730	42.7	4"
EAW-VD9116Z177F7-632AXSP06	432.00	667.2	513.1	575.3	-	433.5	662.3	510.9	570.9	-	609	30.4	4"	487	23.2	3"	730	42.7	4"
EAW-VD9116Z24716-425AXSP04	386.00	626.5	471.6	535.6	-	392.7	626.2	474.5	535.4	-	609	21	4"	487	17	3"	730	29.6	4"
EAW-VD9116Z24716-432AXSP04	353.90	581.4	436.5	496.5	999.1	361.2	581.2	438.9	496.3	989.4	609	21	4"	487	17	3"	730	29.6	4"
EAW-VD9116Z24716-525AXSP04	427.00	689.1	521.9	590.2	1162.6	435.5	688.6	524.7	590.7	1150.1	755	22.3	4"	604	14.7	4"	906	27.5	(2) 4"
EAW-VD9116Z24716-532AXSP04	397.70	650	489.9	555.3	1104.7	406.3	649.2	492.5	556.5	1092.9	755	22.3	4"	604	14.7	4"	906	27.5	(2) 4"
EAW-VD9116Z24716-625AXSP04	460.20	737.9	560.8	634.1	1230.2	469.1	736.4	563.4	633.6	1215.2	913	20	(2) 4"	730	15.7	4"	1096	28.1	(2) 4"
EAW-VD9116Z24716-632AXSP06	472.30	731.1	561.5	630.3	-	473.3	726.7	559.2	625.4	-	609	30.4	4"	487	23.2	3"	730	42.7	4"
EAW-VD9116Z320P5-425AXSP04	420.00	682	512.9	582.6	-	427.4	681.7	515.3	583.4	-	609	21	4"	487	17	3"	730	29.6	4"
EAW-VD9116Z320P5-432AXSP04	384.10	630.2	472	536.8	-	391.1	630	474.5	537.8	-	609	21	4"	487	17	3"	730	29.6	4"
EAW-VD9116Z320P5-525AXSP04	470.60	757.5	573.4	649.3	-	478.4	756.5	575.3	648.6	-	755	22.3	4"	604	14.7	4"	906	27.5	(2) 4"
EAW-VD9116Z320P5-532AXSP04	434.80	708.8	533.9	606.2	1209.2	442.8	707.7	536.7	606.4	1195.6	755	22.3	4"	604	14.7	4"	906	27.5	(2) 4"
EAW-VD9116Z320P5-625AXSP04	511.10	817.4	621.9	702	1368.1	520.2	815.3	624.6	701.3	1351.9	913	20	(2) 4"	730	15.7	4"	1096	28.1	(2) 4"
EAW-VD9116Z320P5-632AXSP04	477.90	775.2	586.5	663.4	1308.8	487.1	773.8	589	663.4	1293.3	913	20	(2) 4"	730	15.7	4"	1096	28.1	(2) 4"
EAW-VD9116Z320P7-425AXSP04	428.20	695.7	523.7	593.9	-	435.6	695.8	525.5	595.1	-	609	21	4"	487	17	3"	730	29.6	4"
EAW-VD9116Z320P7-432AXSP04	391.90	642.7	481.3	547.4	-	399.2	642.8	484.1	548.3	-	609	21	4"	487	17	3"	730	29.6	4"
EAW-VD9116Z320P7-525AXSP04	479.60	772.9	584.7	661.2	-	487.9	772.1	586.9	660.8	-	755	22.3	4"	604	14.7	4"	906	27.5	(2) 4"
EAW-VD9116Z320P7-532AXSP04	443.50	722.7	543.9	617.7	1232.3	452	722.1	547.2	618.4	1220.9	755	22.3	4"	604	14.7	4"	906	27.5	(2) 4"
EAW-VD9116Z320P7-625AXSP04	520.60	833.4	633.7	715.5	1395.5	530.2	831.7	635.9	715.1	1379.7	913	20	(2) 4"	730	15.7	4"	1096	28.1	(2) 4"
EAW-VD9116Z320P7-632AXSP04	487.00	789.7	598	676.6	1334.3	496.7	788.6	598	676.8	1319	913	20	(2) 4"	730	15.7	4"	1096	28.1	(2) 4"
EAW-VD9118PA177F7-425AXSP04	325.20	527.6	397	450.3	-	331.2	529.4	400.4	452.7	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD9118PA177F7-432AXSP04	301.00	492.3	369	419.8	-	306.9	493.5	371.9	421.5	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD9118PA177F7-525AXSP04	360.10	578.5	438	495.1	-	367.4	580.1	441.1	497.3	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA177F7-532AXSP04	337.40	548.4	412.9	468.8	934.7	344.8	549.6	416.5	470.7	927.7	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA177F7-625AXSP04	382.40	610.3	464.5	524.3	1021.3	390.9	611.6	468.5	526.1	1012.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA177F7-632AXSP04	363.70	588.2	445.6	504.1	992.1	372.1	589.6	449.3	506.1	985.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA24716-425AXSP04	351.20	571.5	429.8	488.4	-	358.1	574.1	433.2	490.6	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD9118PA24716-432AXSP04	324.40	532.2	398.3	453.1	-	331.1	533.3	401.7	455.4	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD9118PA24716-525AXSP04	390.90	629.2	475.5	538.3	-	398.7	630.5	479.3	540.3	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA24716-532AXSP04	365.70	593.8	446.9	507.4	-	373.7	595.8	450.6	510	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA24716-625AXSP04	417.70	666.5	506.5	571.6	1118.1	426.8	668.4	510.7	574	1110.8	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA24716-632AXSP04	395.60	639	484.1	547.5	1082.7	404.6	640.9	487.6	550	1074.7	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA320P5-425AXSP02	-	546.7	377.1	451.3	1004.3	-	562.8	399.3	468.2	1007.4	902	10.7	(2) 4"	721	9.4	4"	1082	15	(2) 4"
EAW-VD9118PA320P5-432AXSP04	353.50	580.2	433.9	494.2	-	360.3	582.1	437.8	496.3	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD9118PA320P5-525AXSP04	432.40	697.5	526.3	596.1	-	440.8	699.2	530	598.5	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA320P5-532AXSP04	402.20	654.5	492	558.7	-	410	655.5	495.1	560.5	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA320P5-625AXSP04	467.00	745.2	564.9	638.5	-	475.5	747.5	569.9	641.5	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA320P5-632AXSP04	439.50	708.7	535.3	606.5	-	448.4	711.1	539.6	608.7	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA320P7-425AXSP02	-	555.5	383.1	458.8	1019.7	303.6	571.6	406	475.7	1023.3	902	10.7	(2) 4"	721	9.4	4"	1082	15	(2) 4"
EAW-VD9118PA320P7-432AXSP04	358.50	589.3	440.2	501.7	-	365.3	591.1	444.1	503.7	-	451	22.7	3"	361	15	3"	541	28.3	4"
EAW-VD9118PA320P7-525AXSP04	438.40	708	533.9	605.8	-	447	709.7	538.6	608.3	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA320P7-532AXSP04	407.90	663.9	498.6	566.4	-	415.7	665.4	503.2	568.7	-	564	20.9	4"	451	16.3	3"	676	29.3	4"
EAW-VD9118PA320P7-625AXSP04	474.20	757.4	574.6	648.7	-	483.3	759.3	578.5	651.3	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA320P7-632AXSP04	446.40	719.2	542.9	615.3	-	454.7	721.7	547.3	617.6	-	676	21.7	4"	541	14.3	4"	812	30.5	4"
EAW-VD9118PA177F7-425AXSP04	351.40	564.5	427.1	483.7	-	356.5	565	428.7	483.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD9118PA177F7-432AXSP04	325.30	526.2	396.1	449.6	-	330.1	526.6	398.2	449.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD9118PA177F7-525AXSP04	390.50	620.3	471	531.9	-	396.2	620.1	473.5	532.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9118PA177F7-532AXSP04	366.90	587.6	444.7	503.3	-	372.3	587.5	446.6	503.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9118PA177F7-625AXSP04	417.10	656.3	502.1	564.5	1090.7	423.3	655.5	503.9	564.5	1079.8	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9118PA177F7-632AXSP04	396.20	631.4	480.5	541.2	1058.2	402.9	630.8	481.9	541.5	1048.5	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9118PA24716-425AXSP02	-	541.4	380.8	450.7	979.8	305.2	554.7	398.6	463.9	979	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9118PA24716-432AXSP04	351.40	569.5	428.4	486.5	-	356.5	570.7	430.7	487.2	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD9118PA24716-525AXSP04	424.00	675.7	512.2	579.1	-	430.7	675.1	514.6	579.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9118PA24716-532AXSP04	397.50	637.9	481.8	545.2	-	403.5	637.9	484.8	546.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9118PA24716-625AXSP04	455.60	717.6	547.5	616.3	-	462.1	717.1	549.9	616.6	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9118PA24716-632AXSP04	431.70	686.9	521.8	589.5	-	438.2	686.9	523.9	589.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9118PA24716-625AXSP02	302.40	596.6	420.2	496.8	1075.9	337	608.4	439	510.1	1074.8	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9118PA320P5-432AXSP02	-	546.5	382.3	454	996.4	305	559.4	400.3	467.5	997.1	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9118PA320P5-525AXSP04	468.10	748.4	566.7	640.9	-	474.9	747.4	569.2	640.9	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9118PA320P5-532AXSP04	435.30	700.6	528.5	599.3	-	441	700.5	530.9	600.2	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9118PA320P5-625AXSP04	506.50	800.8	609.7	687.2	-	513.3	800.4	612.5	687.8	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9118PA320P5-632AXSP04	477.30	760.3	577.1	651.9	-	483.7	760	579.3	651.6	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9118PA320P7-425AXSP02	308.30	606.5	427.7	505.2	1094	343	618.3	446.1	518.6	1093.7	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9118PA320P7-432AXSP02	-	556.4	388.8	461.3</															

EAW-VD9118J24716-532AXSP04	460.80	739.2	559.8	633	1249.7	466.9	737	561.5	632.1	1236.3	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9118J24716-625AXSP04	532.80	838.8	641.8	721.2	1390.5	540.1	835.8	642.7	719.6	1373.5	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9118J24716-632AXSP04	502.80	801.4	610.2	687.8	1340.7	510.2	799	611.7	686.8	1324.1	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9118J320P5-425AXSP04	482.70	776.3	585.8	663.7	-	488.2	774.5	587.2	663.2	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9118J320P5-432AXSP04	442.80	716.9	539.3	612.4	-	448	715.2	540.9	610.9	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9118J320P5-525AXSP04	542.40	862.3	654.7	739.7	-	548.1	859.7	655.5	737.5	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9118J320P5-532AXSP04	503.40	806.4	610.5	690.2	-	509.2	803.7	611.2	689	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9118J320P5-625AXSP04	591.20	929.5	710	798.8	-	597.5	925.6	710.7	796.6	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9118J320P5-632AXSP04	553.40	880.9	670.5	756.7	1480.1	560.7	877.9	670.9	754.2	1460.6	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9118J320P7-425AXSP04	491.80	792	598.2	676.7	-	497.7	790.6	598.9	676.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9118J320P7-432AXSP04	451.30	731.2	550	624.2	-	456.9	729.7	551.3	624.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9118J320P7-525AXSP04	552.90	878.6	667.6	753.3	-	559.1	876.4	667.7	751.5	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9118J320P7-532AXSP04	512.60	822.3	622	703.4	-	519	820.2	623.2	702.8	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9118J320P7-625AXSP04	602.30	947.7	723.5	814.2	-	609.2	944.3	724.7	812.4	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9118J320P7-632AXSP04	564.10	898.7	682.5	770.6	1508.9	571.8	896	684.4	769.5	1491.5	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120PA177F7-425AXSP04	368.30	592.3	447.1	506.8	-	373.7	593.2	449.8	507.5	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD9120PA177F7-432AXSP04	340.90	552.2	415.7	471.7	-	346.2	553.4	417.9	472.9	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD9120PA177F7-525AXSP04	408.50	648.5	493.1	556.2	-	414.4	649.2	495.6	557.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9120PA177F7-532AXSP04	383.60	615.3	465.4	526.4	-	389.5	615.5	467.7	527.4	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9120PA177F7-625AXSP04	435.50	684.5	523	589.1	-	442.1	684.9	525.9	589.4	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA177F7-632AXSP04	414.50	660.2	501.5	566.2	1108.1	421.7	660.7	504.7	567.4	1099.6	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA24716-425AXSP02	-	568.3	399.8	472.8	1026.3	321	581.4	418.6	486.9	1025.9	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9120PA24716-432AXSP04	367.70	597.2	448.5	509.3	-	373.3	598.2	451.2	510.7	-	451	24.7	3"	361	16.3	3"	541	31.1	4"
EAW-VD9120PA24716-525AXSP04	442.90	705.6	535.5	605	-	449.9	706.9	537.9	606.1	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9120PA24716-532AXSP04	414.70	666.5	503.1	569.9	-	421.6	667.4	506.2	571.6	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9120PA24716-625AXSP04	474.50	747.7	570.5	642.5	-	481.6	748.7	573.4	643.3	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA24716-632AXSP04	451.30	717.5	545	615.1	-	458	718.4	548	615.9	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA320P5-425AXSP02	320.00	625.7	442.5	522.2	1129.7	355	639	461.9	536.4	1130.9	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9120PA320P5-432AXSP02	-	575.8	402.6	477.8	1047.8	321.5	588.6	421.5	491.9	1048.2	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9120PA320P5-525AXSP02	-	694.4	490.1	578.7	1244.8	394.9	710.1	513.3	595.4	1244.4	1127	12.4	(2) 4"	902	8.1	(2) 4"	1352	17.4	(2) 4"
EAW-VD9120PA320P5-532AXSP04	455.40	733.7	553.1	627.8	-	461.7	734.6	556.5	628.5	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9120PA320P5-625AXSP04	528.40	836.3	636.6	718	-	536.8	837.6	640	719.1	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA320P5-632AXSP04	498.30	796	603	681.8	-	505.3	796.1	605.6	682.9	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA320P7-425AXSP02	325.80	635.2	449.7	530.4	1147.2	360.7	648.8	469.2	545.1	1146.8	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9120PA320P7-432AXSP02	-	584.3	409	485.1	1063.6	327.1	597.9	428.2	499.3	1064.9	902	11.7	(2) 4"	721	10	4"	1082	16.4	(2) 4"
EAW-VD9120PA320P7-525AXSP02	-	705.7	498.1	587.8	1264.1	401.6	721.7	521.5	604.8	1263.6	1127	12.4	(2) 4"	902	8.1	(2) 4"	1352	17.4	(2) 4"
EAW-VD9120PA320P7-532AXSP04	461.80	745.5	567.7	636.5	-	469.1	745.7	564.5	637.7	-	564	22.9	4"	451	17.6	3"	676	32.1	4"
EAW-VD9120PA320P7-625AXSP04	536.60	850	646.6	729.5	-	544.9	850.8	649.8	730.2	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA320P7-632AXSP04	505.20	807.9	611.6	691.7	-	513.3	808.1	615.4	692.9	-	676	23.7	4"	541	15.6	4"	812	33.3	4"
EAW-VD9120PA177F7-425AXSP04	431.50	690.8	523.2	591.4	-	436.9	689.4	524.4	591.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA177F7-432AXSP04	398.50	643.9	485.2	549.8	-	404.3	642.5	486.4	549.5	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA177F7-525AXSP04	477.90	758.2	576.6	650.2	-	484.6	755.5	578.5	649.8	1254.9	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA177F7-532AXSP04	446.40	717.1	542.9	613.5	1210.8	453	714.9	544.5	612.7	1196.3	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA177F7-625AXSP04	513.50	808.3	619.1	695.4	1337.3	520.6	805.7	620.1	694.1	1321.5	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA177F7-632AXSP04	485.60	774.9	589.8	665.5	1295.1	493.6	772.9	591.4	664.7	1279.6	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA24716-425AXSP04	468.90	753.9	568.7	645	-	475	752.2	571.1	644.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA24716-432AXSP04	432.80	700.1	526.8	598.4	-	438.4	699.3	529.2	597.7	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA24716-525AXSP04	521.80	829.1	629.4	710.8	-	528.2	827	631.4	710	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA24716-532AXSP04	487.60	780.8	590.9	668.8	-	494	779.7	592.7	667.9	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA24716-625AXSP04	562.90	885.7	677.6	761.9	1472	571	884.2	678.9	760.5	1454.8	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA24716-632AXSP04	531.40	846.7	644.4	726.9	1418.9	539.2	845.3	646	725.8	1404.7	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA320P5-425AXSP04	510.90	823.3	620.6	703.9	-	517.3	821	623	703.1	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA320P5-432AXSP04	468.30	759.6	570.8	648	-	474.1	758.9	572.7	648.2	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA320P5-525AXSP04	573.80	913.7	693.3	782.8	-	579.9	911.1	694.2	781.8	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA320P5-532AXSP04	532.10	854.5	646.3	731.4	-	539.4	853	647	730.2	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA320P5-625AXSP04	625.50	984.4	750.6	846.3	-	632.5	982.1	752.8	844.3	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA320P5-632AXSP04	586.10	932.9	708.5	800.4	-	593.8	931.1	710.1	798.9	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA320P7-425AXSP02	-	740.7	520.6	615.8	1339.1	416.6	755.6	544.3	632.9	1334.8	1217	12.8	(2) 4"	974	8.4	(2) 4"	1461	17.9	(2) 4"
EAW-VD9120ZA320P7-432AXSP04	476.70	773.8	581.3	660.3	-	483.1	773.6	583.7	660.4	-	609	23.3	4"	487	18.4	3"	730	32.7	4"
EAW-VD9120ZA320P7-525AXSP04	583.00	929.6	704.7	796	-	590.7	927.5	707.3	795.4	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA320P7-532AXSP04	541.80	869.6	657.1	744	-	548.5	868.5	659.4	744.3	-	755	24.5	4"	604	16.1	4"	906	30.6	(2) 4"
EAW-VD9120ZA320P7-625AXSP04	636.00	1001.8	764.6	861	-	643.5	999.8	766	859.3	-	913	22.3	(2) 4"	730	17.2	4"	1096	31.2	(2) 4"
EAW-VD9120ZA320P7-632AXSP04	597.40	950.2	721.2	815	-	604.7	947.5	723.3	813.9	-	913	22.3	(2) 4"	730	17.2</				

EAW-VD91S3MA24716-525AXSP12	77.90	123.6	93.9	106	-	78.8	123.3	94.2	105.9	-	113	26.1	1-1/2"	90	17.2	1-1/2"	135	36.7	1-1/2"
EAW-VD91S3MA24716-532AXSP12	72.70	116.6	88.3	99.9	-	73.8	116.4	88.6	99.8	-	113	26.1	1-1/2"	90	17.2	1-1/2"	135	36.7	1-1/2"
EAW-VD91S3MA320P5-425AXSP08	65.00	115.1	84.3	97.6	202.3	68.6	116.2	86.1	98.8	201.1	146	16	2"	117	12.8	1-1/2"	176	22.5	2"
EAW-VD91S3MA320P5-432AXSP12	69.80	113.3	85.1	96.7	-	70.7	113	85.4	96.5	-	90	25	1-1/2"	72	16.5	1-1/2"	108	35.1	1-1/2"
EAW-VD91S3MA320P5-525AXSP12	85.60	136.3	103.4	116.8	-	86.7	136.1	103.8	116.8	-	113	26.1	1-1/2"	90	17.2	1-1/2"	135	36.7	1-1/2"
EAW-VD91S3MA320P5-532AXSP12	79.50	127.8	96.5	109.2	-	80.6	127.6	96.9	109.3	-	113	26.1	1-1/2"	90	17.2	1-1/2"	135	36.7	1-1/2"
EAW-VD91S3MA320P7-425AXSP08	66.30	117	85.9	99.4	206	70	118.3	87.8	100.5	204.9	146	16	2"	117	12.8	1-1/2"	176	22.5	2"
EAW-VD91S3MA320P7-432AXSP12	71.00	115.3	86.7	98.4	-	72	115.1	86.9	98.5	-	90	25	1-1/2"	72	16.5	1-1/2"	108	35.1	1-1/2"
EAW-VD91S3MA320P7-525AXSP12	87.10	138.7	105.3	118.9	-	88.1	138.5	105.5	118.8	-	113	26.1	1-1/2"	90	17.2	1-1/2"	135	36.7	1-1/2"
EAW-VD91S3MA320P7-532AXSP12	80.90	130	98.3	111.3	-	82	129.9	98.5	111.2	-	113	26.1	1-1/2"	90	17.2	1-1/2"	135	36.7	1-1/2"
EAW-VD91S4MA177F7-425AXSP08	81.20	134	100.7	114.4	229.5	83.3	134.3	101.4	114.8	227.6	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA177F7-432AXSP08	74.70	124.8	93.2	106.4	215.4	76.7	125	94.1	106.8	213.4	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA177F7-525AXSP08	88.90	146.1	110.1	125.1	247.5	91.5	146.3	111.1	125.5	245.4	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA177F7-532AXSP08	82.90	138.2	103.4	118.1	236	85.5	138.4	104.5	118.5	233.7	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA24716-425AXSP08	88.70	146	109.4	124.5	-	90.9	146.3	110.4	125	-	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA24716-432AXSP08	81.40	135.6	101.4	115.6	234.5	83.6	136.2	102.4	116	232.7	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA24716-525AXSP08	97.60	159.8	120.4	136.6	271.2	100	160	121.5	137	269.1	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA24716-532AXSP08	90.70	150.5	112.8	128.5	257.6	93.2	150.9	113.9	129.1	255.7	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA320P5-425AXSP08	97.20	159.6	119.5	136	-	99.3	159.9	120.6	136.5	-	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA320P5-432AXSP08	88.70	147.3	109.9	125.3	-	90.8	147.6	110.9	125.8	-	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA320P5-525AXSP08	107.80	176.3	132.7	150.5	300.3	110.4	176.4	133.7	150.9	297.7	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA320P5-532AXSP08	99.60	164.8	123.6	140.6	283.3	102.1	165.3	124.6	141	280.6	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA320P7-425AXSP08	98.90	162.4	121.7	138.5	-	101.1	163	122.6	139.1	-	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA320P7-432AXSP08	90.30	149.9	112	127.6	-	92.5	150.3	112.9	128.2	-	146	20	2"	117	15.5	1-1/2"	176	28.1	2"
EAW-VD91S4MA320P7-525AXSP08	109.80	179.2	135	153.2	-	112.3	179.7	136.1	153.7	-	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S4MA320P7-532AXSP08	101.40	167.6	125.8	143.2	288.4	104	168.2	126.9	143.7	285.8	180	21	2"	144	13.8	2"	216	29.5	2"
EAW-VD91S5MA177F7-425AXSP08	107.00	171.3	129.6	146.7	-	108.4	171	129.9	146.4	-	146	24	2"	117	18.1	1-1/2"	176	33.7	2"
EAW-VD91S5MA177F7-432AXSP08	99.00	159.6	120.3	136.3	-	100.2	159.3	120.6	136.2	-	146	24	2"	117	18.1	1-1/2"	176	33.7	2"
EAW-VD91S5MA177F7-525AXSP08	118.10	186.8	142.3	160.2	-	119.6	186.3	142.6	160.2	-	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA177F7-532AXSP08	110.40	176.6	133.8	151.3	298.3	111.9	176.2	134.4	151.2	295	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA24716-425AXSP08	116.20	186.5	141	159.6	-	117.8	186.5	141.6	159.5	-	146	24	2"	117	18.1	1-1/2"	176	33.7	2"
EAW-VD91S5MA24716-432AXSP08	107.30	173.4	130.6	148.2	-	108.7	173.3	131.1	148.1	-	146	24	2"	117	18.1	1-1/2"	176	33.7	2"
EAW-VD91S5MA24716-525AXSP08	128.70	204.2	155.2	175	-	130.3	203.8	155.5	174.9	-	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA24716-532AXSP08	120.30	192.4	145.6	164.8	-	121.7	192.2	146.1	164.6	-	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA320P5-425AXSP06	117.10	194.9	145.5	165.8	-	120.5	195.7	147	166.9	-	192	19.8	2"	153	13.1	2"	230	27.9	2"
EAW-VD91S5MA320P5-432AXSP08	116.30	188.5	141.8	160.8	-	117.8	188	142.1	160.9	-	146	24	2"	117	18.1	1-1/2"	176	33.7	2"
EAW-VD91S5MA320P5-525AXSP08	141.50	225.1	170.7	193.1	-	143.1	224.5	171.3	192.6	-	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA320P5-532AXSP08	131.30	210.5	159.2	180.2	-	132.9	210.3	159.7	180.3	-	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA320P7-425AXSP06	119.30	198.3	148.1	168.9	-	122.6	199.2	149.7	169.7	-	192	19.8	2"	153	13.1	2"	230	27.9	2"
EAW-VD91S5MA320P7-432AXSP08	118.30	191.8	144.3	163.7	-	119.9	191.5	144.8	163.8	-	146	24	2"	117	18.1	1-1/2"	176	33.7	2"
EAW-VD91S5MA320P7-525AXSP08	143.90	229.2	173.7	196.2	-	145.6	228.7	174.4	196.1	-	180	25	2"	144	16.5	2"	216	35.1	2"
EAW-VD91S5MA320P7-532AXSP08	133.60	214.5	162	183.5	-	135.3	214	162.7	183.4	-	180	25	2"	144	16.5	2"	216	35.1	2"