

UNIT	CLOSED CIRCUIT COOLER		DWG. #	WLEP83610-DRC-SR	REV.	-
MODEL #	LSWE 10-3K18	SCALE NTS	SERIAL #		DATE	3/29/2024


EVAPCO, INC.

NOTES:
1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
   FPT DENOTES FEMALE PIPE THREAD
   BFW DENOTES BEVELED FOR WELDING
   GVD DENOTES GROOVED
   FLG DENOTES FLANGE
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. HEAVIEST SECTION IS COIL SECTION
8. THE SPRAY PUMP SHOULD BE SIZED FOR 840 gpm [63.6 l/s] AND 2.5 psi [17.2 kPa] AT THE INLET CONNECTION(S)
9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS
10. VENT PROVIDED ON CLOSED CIRCUIT COOLERS ONLY

PLAN VIEW







Preliminary

SHIPPING WEIGHT	18660 lbs+ [8465] kg+	OPERATING WEIGHT	28410 lbs+ [12890] kg+	HEAVIEST SECTION WEIGHT	11530 lbs+ [5230] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	TLS