UNIT	COOLING TOWER		EVAPCO, INC.	DWG. #	T3121236-DRD-ST	REV.	-
MODEL #	AT 112-3M12	SCALE	NTS	SERIAL #		DATE	7/13/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
   FPT DENOTES FEMALE PIPE THREAD
   BFW DENOTES BEVELED FOR WELDING
   GVD DENOTES GROOVED
   FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
   20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES.
   REFER TO RECOMMENDED STEEL SUPPORT DRAWING
7. DIMENSIONS LISTED AS FOLLOWS:
   ENGLISH FT-IN
   [METRIC] [mm]

FACE C



FACE B

PLAN VIEW

FACE D

FACE A



FACE B



FACE A

Preliminary

SHIPPING WEIGHT	8140 lbs+ [3695] kg+	OPERATING WEIGHT	14350 lbs+ [6510] kg+	HEAVIEST SECTION WEIGHT	5740 lbs+ [2605] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	KDS