



NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

**FACE 2  
PLAN VIEW**

24'-1 1/8" [ 7344 ]

69 3/8 [ 1762 ]

5 1/8 [ 130 ]

27 5/8 \* [ 702 ]

56 1/4 [ 1427 ]

(4) 4 [100] BFW INLET 113 3/4 \* [ 2888 ]

44 3/8 \* [ 1126 ]

75 1/32 [ 1906 ]

(4) 4 [100] BFW OUTLET

98 1/8 [ 2492 ]

5 1/2 [ 140 ]

33 1/2 \* [ 851 ]

5 1/2 [ 140 ]

5 7/8 \* [ 149 ]

25 1/4 [ 641 ]

(2) 3 [80] MPT OVERFLOW

(2) 2 [50] MPT MAKE-UP

(2) 3 [80] MPT DRAIN

5 1/4 [ 133 ]

4 1/4 [ 108 ]

142 [ 3607 ]

3 5/8 [ 92 ]

17 [ 432 ]

56 [ 1422 ]

**FACE 1**

(4) 1/2 [15] FPT VENT

CROSSOVER PIPING

ACCESS DOORS

229 5/8 [ 5832 ]

7 [ 178 ]

20 7/8 [ 530 ]

20'-0" [ 6096 ]

**FACE 2**

|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 45030 lbs+ [20430] kg+ | OPERATING WEIGHT | 68230 lbs+ [30950] kg+ | HEAVIEST SECTION WEIGHT | 13920 lbs+ [6315] kg+ | NO. OF SHIPPING SECTIONS | 6 | DRAWN BY: | SFR |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|