

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE 2

Dimensions (English / Metric):

- Total width: 24'-1 1/8" [7344]
- Top section width: 69 3/8" [1762]
- Left side height: 9 1/2" [241]
- Section height: 33 1/2" [851]
- Bottom left height: 5 7/8" [149]
- Bottom left corner offset: 25 1/4" [641]
- Right side height: 27 5/8" [702] *
- Inlet/outlet offset: 56 1/4" [1427]
- Coil section height: 105 3/4" [2684]
- Pipe offset: 36 3/8" [922]
- Coil section height: 100 9/32" [2547]
- Coil section height: 98 1/8" [2492]
- Bottom right offset: 5 1/4" [133]
- Bottom right offset: 4 1/4" [108]
- Bottom right offset: 3 5/8" [92]
- Bottom right offset: 17" [432]
- Bottom right offset: 56" [1422]
- Bottom right offset: 142" [3607]

Labels:

- (2) 3 [80] MPT OVERFLOW
- (2) 2 [50] MPT MAKE-UP
- (2) 3 [80] MPT DRAIN
- (4) 4 [100] BFW INLET
- (4) 4 [100] BFW OUTLET

**FACE 2
PLAN VIEW**

FACE 1

Dimensions (English / Metric):

- Top section height: 7" [178]
- Total height: 230 7/8" [5864]
- Bottom left offset: 18 1/4" [464]
- Bottom right offset: 11'-11 3/4" [3651]

Labels:

- (4) 1/2 [15] FPT VENT
- CROSSOVER PIPING
- ACCESS DOORS

SHIPPING WEIGHT	52290 lbs+ [23720] kg+	OPERATING WEIGHT	71830 lbs+ [32585] kg+	HEAVIEST SECTION WEIGHT	20470 lbs+ [9285] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SRF
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----