| UNIT | | | DWG. # | REV |
|---|---|---|---|---|
| CLOSED CIRCUIT COOLER | **EVAPCO, INC.** | | WX412182408F-DRA-ST | - |
| MODEL # ESW4 12-24J18-LF | SCALE NTS | | SERIAL # | DATE: 2/6/2026 |

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
   FPT DENOTES FEMALE PIPE THREAD
   BFW DENOTES BEVELED FOR WELDING
   GVD DENOTES GROOVED
   FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
   ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.
   REFER TO RECOMMENDED STEEL
   SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
   20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
   ENGLISH FT-IN
   [METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE
   FOR PRE-FABRICATION OF CONNECTING PIPING

**FACE C**

**FACE B**
**PLAN VIEW**




**FACE D**

**FACE A**

Preliminary




**FACE B**




**FACE A**

| SHIPPING WEIGHT | 28220 lbs+ [12805] kg+ | OPERATING WEIGHT | 42370 lbs+ [19220] kg+ | HEAVIEST SECTION WEIGHT | 21620 lbs+ [9810] kg+ | NO. OF SHIPPING SECTIONS | 2 | DRAWN BY: | AWT |
|---|---|---|---|---|---|---|---|---|---|