STD-201RS Dry Table 3a - IP Units - Dry Fluid Coolers (DFC)

8/25/2022

Evapco EAW Line Thermal Performance in USGPM - Water as Process Fluid

Range °F	10	10	15	15	9	10	10	15	15	9	First	First	First	Second	Second	Second	Third	Third	Third
Approach °F	5	10	10	12	18	5	10	10	12	18	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow
Dry Bulb Temperature °F	77	77	77	77	77	95	95	95	95	95	GPM	PSI	Inlet	GPM	PSI	Inlet	GPM	PSI	Inlet
EAW-VD15S1ZB370K4-625AXSP16	-	-	-	-	175.9	-	-	-	-	173.9	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB370K4-525AXSP16	-	100.5	-	-	165.6	-	99.9	-	-	164.1	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB370K4-425AXSP16	-	92.4	-	79.5	154.3	-	91.9	-	79.2	153	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB550K4-625AXSP16	-	122	-	-	199.4	-	121.3	-	-	197.4	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB550K4-525AXSP16	-	112.9	-	97.2	187.1	-	112.3	-	96.8	185.4	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB550K4-425AXSP16	-	103.5	79	88.9	173.6	-	103.1	78.8	88.6	172.2	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB750K4-625AXSP16	-	132.4	-	114.4	217.3	-	131.9	-	113.9	215.4	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB750K4-525AXSP16	-	122.5	93.9	105.4	203.7	-	122	93.7	105.1	202	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB750K4-425AXSP16	-	112.1	85.4	96.2	188.5	-	111.7	85.3	96	187.2	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB370K5-625AXSP16	-	-	-	-	175.9	-	-	-	-	173.9	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB370K5-525AXSP16	-	100.5	-	-	165.6	-	99.9	-	-	164.1	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB370K5-425AXSP16	-	92.4	-	79.5	154.3	-	91.9	-	79.2	153	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB550K5-625AXSP16	-	122	-	-	199.4	-	121.3	-	-	197.4	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB550K5-525AXSP16	-	112.9	-	97.2	187.1	-	112.3	-	96.8	185.4	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB550K5-425AXSP16	-	103.5	79	88.9	173.6	-	103.1	78.8	88.6	172.2	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB750K5-625AXSP16	-	132.4	-	114.4	217.3	-	131.9	-	113.9	215.4	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB750K5-525AXSP16	-	122.5	93.9	105.4	203.7	-	122	93.7	105.1	202	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB750K5-425AXSP16	-	112.1	85.4	96.2	188.5	-	111.7	85.3	96	187.2	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB370C4-625AXSP16	-	113	-	-	184.1	-	112.1	-	-	182	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB370C4-525AXSP16	-	104.7	-	90.2	172.9	-	104	-	89.8	171.3	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB370C4-425AXSP16	-	96.1	73.3	82.5	160.7	-	95.6	73.2	82.2	159.3	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB550C4-625AXSP16	-	128.5	-	-	210.4	-	127.7	-	-	208.2	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB550C4-525AXSP16	-	118.4	90.8	101.9	196.7	-	117.7	90.5	101.5	194.8	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB550C4-425AXSP16	-	108.1	82.4	92.7	181.5	-	107.6	82.1	92.4	180	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB750C4-625AXSP16	-	137.8	-	118.8	226.2	-	137	-	118.4	224.1	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB750C4-525AXSP16	-	127	97.2	109.2	211.4	-	126.5	97	108.9	209.7	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB750C4-425AXSP16	73.7	115.9	88.2	99.5	195.2	73.9	115.6	88.3	99.2	193.9	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB370C5-625AXSP16	-	113	-	-	184.1	-	112.1	-	-	182	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB370C5-525AXSP16	-	104.7	-	90.2	172.9	-	104	-	89.8	171.3	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB370C5-425AXSP16	-	96.1	73.3	82.5	160.7	-	95.6	73.2	82.2	159.3	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB550C5-625AXSP16	-	128.5	-	-	210.4	-	127.7	-	-	208.2	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB550C5-525AXSP16	-	118.4	90.8	101.9	196.7	-	117.7	90.5	101.5	194.8	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB550C5-425AXSP16	-	108.1	82.4	92.7	181.5	-	107.6	82.1	92.4	180	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB750C5-625AXSP16	-	137.8	-	118.8	226.2	-	137	-	118.4	224.1	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB750C5-525AXSP16	-	127	97.2	109.2	211.4	-	126.5	97	108.9	209.7	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB750C5-425AXSP16	73.7	115.9	88.2	99.5	195.2	73.9	115.6	88.3	99.2	193.9	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB370K8-625AXSP16	-	-	-	-	175.9	-	-	-	-	173.9	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB370K8-525AXSP16	-	100.5	-	-	165.6	-	99.9	-	-	164.1	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB370K8-425AXSP16	-	92.4	-	79.5	154.3	-	91.9	-	79.2	153	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB550K8-625AXSP16	-	122	-	-	199.4	-	121.3	-	-	197.4	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB550K8-525AXSP16	-	112.9	-	97.2	187.1	-	112.3	-	96.8	185.4	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB550K8-425AXSP16	-	103.5	79	88.9	173.6	-	103.1	78.8	88.6	172.2	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S1ZB750K8-625AXSP16	-	132.4	-	114.4	217.3	-	131.9	-	113.9	215.4	242	17.4	3"	194	14.4	2"	291	24.4	3"
EAW-VD15S1ZB750K8-525AXSP16	-	122.5	93.9	105.4	203.7	-	122	93.7	105.1	202	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD15S1ZB750K8-425AXSP16	-	112.1	85.4	96.2	188.5	-	111.7	85.3	96	187.2	157	18.7	2"	126	15.2	1-1/2"	189	26.2	2"
EAW-VD15S2ZB370K4-625AXSP12	-	221.5	172.9	192.1	356.4	-	219.2	171.5	190.5	352	327	23.1	3"	262	15.3	3"	392	32.5	3"
EAW-VD15S2ZB370K4-525AXSP08	-	203.1	-	-	334.4	-	201.8	-	-	331.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB370K4-425AXSP08	-	188	-	161.5	313.1	-	186.9	-	160.8	310.3	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB550K4-625AXSP08	-	243.2	-	-	398	-	241.8	-	-	393.8	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB550K4-525AXSP08	-	228.3	-	196.6	378	-	227.1	-	195.8	374.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB550K4-425AXSP08	-	210.5	160.7	180.9	352.4	-	209.6	160.5	180.3	349.6	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB750K4-625AXSP08	-	264.2	-	227.9	433	-	262.9	-	227.3	429.7	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB750K4-525AXSP08	-	248	190.1	213.2	411.5	-	246.6	189.6	212.7	408	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB750K4-425AXSP08	-	228	173.8	195.8	383.4	-	227.3	173.8	195.5	380.2	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB370K5-625AXSP12	-	221.5	172.9	192.1	356.4	-	219.2	171.5	190.5	352	327	23.1	3"	262	15.3	3"	392	32.5	3"
EAW-VD15S2ZB370K5-525AXSP08	-	203.1	-	-	334.4	-	201.8	-	-	331.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB370K5-425AXSP08	-	188	-	161.5	313.1	-	186.9	-	160.8	310.3	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB550K5-625AXSP08	-	243.2	-	-	398	-	241.8	-	-	393.8	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB550K5-525AXSP08	-	228.3	-	196.6	378	-	227.1	-	195.8	374.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB550K5-425AXSP08	-	210.5	160.7	180.9	352.4	-	209.6	160.5	180.3	349.6	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB750K5-625AXSP08	-	264.2	-	227.9	433	-	262.9	-	227.3	429.7	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB750K5-525AXSP08	-	248	190.1	213.2	411.5	-	246.6	189.6	212.7	408	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB750K5-425AXSP08	-	228	173.8	195.8	383.4	-	227.3	173.8	195.5	380.2	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB370C4-625AXSP08	-	225.3	-	-	367.3	-	-	-	-	363.2	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB370C4-525AXSP08	-	211.8	-	-	349.6	-	210.5	-	-	346	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB370C4-425AXSP08	-	195.4	-	167.9	326.2	-	194.2	-	167.1	323.2	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB550C4-625AXSP08	-	256.1	-	-	419.4	-	254.5	-	-	415.4	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB550C4-525AXSP08	-	239.7	-	206.2	397.3	-	238.3	-	205.4	393.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB550C4-425AXSP08	-	219.9	167.5	188.7	368.7	-	218.8	167.3	188.1	365.5	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB750C4-625AXSP08	-	274.6	-	237	450.8	-	273.3	-	235.9	447.2	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB750C4-525AXSP08	-	257.2	196.8	220.9	427.1	-	255.8	196.7	220.4	424.1	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB750C4-425AXSP08	-	235.9	179.8	202.4	397.2	-	235.1	179.6	202.1	393.8	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB370C5-625AXSP08	-	225.3	-	-	367.3	-	-	-	-	363.2	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB370C5-525AXSP08	-	211.8	-	-	349.6	-	210.5	-	-	346	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB370C5-425AXSP08	-	195.4	-	167.9	326.2	-	194.2	-	167.1	323.2	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB550C5-625AXSP08	-	256.1	-	-	419.4	-	254.5	-	-	415.4	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB550C5-525AXSP08	-	239.7	-	206.2	397.3	-	238.3	-	205.4	393.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB550C5-425AXSP08	-	219.9	167.5	188.7	368.7	-	218.8	167.3	188.1	365.5	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB750C5-625AXSP08	-	274.6	-	237	450.8	-	273.3	-	235.9	447.2	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB750C5-525AXSP08	-	257.2	196.8	220.9	427.1	-	255.8	196.7	220.4	424.1	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB750C5-425AXSP08	-	235.9	179.8	202.4	397.2	-	235.1	179.6	202.1	393.8	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB370K8-625AXSP12	-	221.5	172.9	192.1	356.4	-	219.2	171.5	190.5	352	327	23.1	3"	262	15.3	3"	392	32.5	3"
EAW-VD15S2ZB370K8-525AXSP08	-	203.1	-	-	334.4	-	201.8	-	-	331.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB370K8-425AXSP08	-	188	-	161.5	313.1	-	186.9	-	160.8	310.3	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB550K8-625AXSP08	-	243.2	-	-	398	-	241.8	-	-	393.8	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB550K8-525AXSP08	-	228.3	-	196.6	378	-	227.1	-	195.8	374.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB550K8-425AXSP08	-	210.5	160.7	180.9	352.4	-	209.6	160.5	180.3	349.6	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S2ZB750K8-625AXSP08	-	264.2	-	227.9	433	-	262.9	-	227.3	429.7	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD15S2ZB750K8-525AXSP08	-	248	190.1	213.2	411.5	-	246.6	189.6	212.7	408	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD15S2ZB750K8-425AXSP08	-	228	173.8	195.8	383.4	-	227.3	173.8	195.5	380.2	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD15S3ZB370K4-625AXSP08	-	330	257.5	286.1	531.8	-	326.9	255.7	283.8	525.8	484	24.4	3"	388	16.1	3"	581	30.1	4"
EAW-VD15S3ZB370K4-525AXSP06	-	309.3	-	266.8	507	-	306.9	-	265.4	501.8	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB370K4-425AXSP06	-	283.3	217.2	243.7	471	-	281.6	216.4	242.6	466.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB550K4-625AXSP06	-	368.8	-	318.7	600.3	-	366.2	-	316.8	594	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB550K4-525AXSP06	-	347.9	267.7	299.9	573.2	-	345.6	267.1	298.7	567.8	545	16.8	4"	436	13.4	3"	654	23.6	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3ZB550K4-425AXSP06	203.6	317.2	242.6	273	530.1	203.7	315.7	242	271.8	525.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB750K4-625AXSP06	-	400.3	309.5	345.9	654	-	398.2	308.7	344.5	648.3	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB750K4-525AXSP06	-	377.6	290.3	325.5	624.2	-	375.9	289.5	324	618.9	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB750K4-425AXSP06	219.9	344.2	262.9	295.7	575.9	220.4	342.4	262.1	294.7	571.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB370K5-625AXSP08	-	330	257.5	286.1	531.8	-	326.9	255.7	283.8	525.8	484	24.4	3"	388	16.1	3"	581	30.1	4"
EAW-VD15S3ZB370K5-525AXSP06	-	309.3	-	266.8	507	-	306.9	-	265.4	501.8	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB370K5-425AXSP06	-	283.3	217.2	243.7	471	-	281.6	216.4	242.6	466.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB550K5-625AXSP06	-	368.8	-	318.7	600.3	-	366.2	-	316.8	594	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB550K5-525AXSP06	-	347.9	267.7	299.9	573.2	-	345.6	267.1	298.7	567.8	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB550K5-425AXSP06	203.6	317.2	242.6	273	530.1	203.7	315.7	242	271.8	525.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB750K5-625AXSP06	-	400.3	309.5	345.9	654	-	398.2	308.7	344.5	648.3	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB750K5-525AXSP06	-	377.6	290.3	325.5	624.2	-	375.9	289.5	324	618.9	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB750K5-425AXSP06	219.9	344.2	262.9	295.7	575.9	220.4	342.4	262.1	294.7	571.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB370C4-625AXSP08	229.9	344.8	268.7	298.7	556.5	229.1	341.6	266.9	296.6	550.2	484	24.4	3"	388	16.1	3"	581	30.1	4"
EAW-VD15S3ZB370C4-525AXSP06	-	322.3	-	278.1	530	-	320.1	-	276.7	524.5	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB370C4-425AXSP06	-	294.3	225.4	253.4	490	-	292.5	224.8	251.8	485.4	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB550C4-625AXSP06	-	387.9	-	335.3	633.5	-	385.5	-	333.7	627.4	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB550C4-525AXSP06	-	365.3	280.7	314.6	602.6	-	362.8	280	313.3	596.7	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB550C4-425AXSP06	212.2	331.4	253.4	284.9	554.6	212.2	329.7	252.7	283.5	549	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB750C4-625AXSP06	-	416	321.7	359.2	680.9	-	413.6	320.8	357.6	674.6	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB750C4-525AXSP06	253.4	391.6	301.1	337.3	648.8	254	390	300.4	336.4	643.4	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB750C4-425AXSP06	227.1	356.1	271.6	305.7	596.6	227.6	354.3	271.2	304.6	591.6	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB370C5-625AXSP08	229.9	344.8	268.7	298.7	556.5	229.1	341.6	266.9	296.6	550.2	484	24.4	3"	388	16.1	3"	581	30.1	4"
EAW-VD15S3ZB370C5-525AXSP06	-	322.3	-	278.1	530	-	320.1	-	276.7	524.5	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB370C5-425AXSP06	-	294.3	225.4	253.4	490	-	292.5	224.8	251.8	485.4	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB550C5-625AXSP06	-	387.9	-	335.3	633.5	-	385.5	-	333.7	627.4	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB550C5-525AXSP06	-	365.3	280.7	314.6	602.6	-	362.8	280	313.3	596.7	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB550C5-425AXSP06	212.2	331.4	253.4	284.9	554.6	212.2	329.7	252.7	283.5	549	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB750C5-625AXSP06	-	416	321.7	359.2	680.9	-	413.6	320.8	357.6	674.6	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB750C5-525AXSP06	253.4	391.6	301.1	337.3	648.8	254	390	300.4	336.4	643.4	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB750C5-425AXSP06	227.1	356.1	271.6	305.7	596.6	227.6	354.3	271.2	304.6	591.6	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB370K8-625AXSP08	-	330	257.5	286.1	531.8	-	326.9	255.7	283.8	525.8	484	24.4	3"	388	16.1	3"	581	30.1	4"
EAW-VD15S3ZB370K8-525AXSP06	-	309.3	-	266.8	507	-	306.9	-	265.4	501.8	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB370K8-425AXSP06	-	283.3	217.2	243.7	471	-	281.6	216.4	242.6	466.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB550K8-625AXSP06	-	368.8	-	318.7	600.3	-	366.2	-	316.8	594	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB550K8-525AXSP06	-	347.9	267.7	299.9	573.2	-	345.6	267.1	298.7	567.8	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB550K8-425AXSP06	203.6	317.2	242.6	273	530.1	203.7	315.7	242	271.8	525.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S3ZB750K8-625AXSP06	-	400.3	309.5	345.9	654	-	398.2	308.7	344.5	648.3	654	17.6	4"	523	11.6	4"	785	24.7	4"
EAW-VD15S3ZB750K8-525AXSP06	-	377.6	290.3	325.5	624.2	-	375.9	289.5	324	618.9	545	16.8	4"	436	13.4	3"	654	23.6	4"
EAW-VD15S3ZB750K8-425AXSP06	219.9	344.2	262.9	295.7	575.9	220.4	342.4	262.1	294.7	571.1	436	18.5	3"	349	12.2	3"	523	22.7	4"
EAW-VD15S4ZB370K4-625AXSP06	-	441	344.1	382.4	710.6	-	436.9	341.8	379.3	702.5	654	22.1	4"	523	14.6	4"	785	31	4"
EAW-VD15S4ZB370K4-525AXSP04	-	406.1	-	-	669.7	-	403.5	-	-	662.8	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB370K4-425AXSP04	-	372.8	-	320.5	622.2	-	370.7	-	319.2	616.7	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB550K4-625AXSP04	-	485.8	-	-	795	-	483	-	-	787.6	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB550K4-525AXSP04	-	456.6	-	393.2	756	-	454.2	-	391.7	748.9	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB550K4-425AXSP04	-	417.9	318.7	358.9	700.1	-	416.1	318	357.3	694.5	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB750K4-625AXSP04	-	527.8	-	455.2	866	-	525.1	-	454	858.5	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB750K4-525AXSP04	-	496	380.1	426.5	823	-	493.9	379.2	425.3	817	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB750K4-425AXSP04	-	452.6	344.5	388.5	760.4	-	451.1	344.2	387.2	755.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB370K5-625AXSP06	-	441	344.1	382.4	710.6	-	436.9	341.8	379.3	702.5	654	22.1	4"	523	14.6	4"	785	31	4"
EAW-VD15S4ZB370K5-525AXSP04	-	406.1	-	-	669.7	-	403.5	-	-	662.8	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB370K5-425AXSP04	-	372.8	-	320.5	622.2	-	370.7	-	319.2	616.7	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB550K5-625AXSP04	-	485.8	-	-	795	-	483	-	-	787.6	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB550K5-525AXSP04	-	456.6	-	393.2	756	-	454.2	-	391.7	748.9	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB550K5-425AXSP04	-	417.9	318.7	358.9	700.1	-	416.1	318	357.3	694.5	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB750K5-625AXSP04	-	527.8	-	455.2	866	-	525.1	-	454	858.5	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB750K5-525AXSP04	-	496	380.1	426.5	823	-	493.9	379.2	425.3	817	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB750K5-425AXSP04	-	452.6	344.5	388.5	760.4	-	451.1	344.2	387.2	755.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB370C4-625AXSP06	307.7	461.3	359.2	399.8	744.4	306.2	457	356.8	396.5	735.2	654	22.1	4"	523	14.6	4"	785	31	4"
EAW-VD15S4ZB370C4-525AXSP04	-	423.6	-	-	699.1	-	420.9	-	-	692	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB370C4-425AXSP04	-	387.3	-	333.2	648.1	-	385.6	-	331.7	642.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB550C4-625AXSP04	-	511.5	-	-	838.9	-	508.5	-	-	830.8	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB550C4-525AXSP04	-	479.3	-	412.4	794.5	-	476.7	-	410.7	787.8	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB550C4-425AXSP04	-	436.5	332.3	374.4	732.3	-	434.3	331.9	373.2	726.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB750C4-625AXSP04	-	548.4	-	473.3	901.6	-	546	-	471.9	893.3	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB750C4-525AXSP04	-	514.3	393.7	441.9	855.3	-	512.3	393.5	440.8	848.3	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB750C4-425AXSP04	-	468.2	356.5	401.5	787.6	-	466.6	356.1	400.9	782.2	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB370C5-625AXSP06	307.7	461.3	359.2	399.8	744.4	306.2	457	356.8	396.5	735.2	654	22.1	4"	523	14.6	4"	785	31	4"
EAW-VD15S4ZB370C5-525AXSP04	-	423.6	-	-	699.1	-	420.9	-	-	692	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB370C5-425AXSP04	-	387.3	-	333.2	648.1	-	385.6	-	331.7	642.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB550C5-625AXSP04	-	511.5	-	-	838.9	-	508.5	-	-	830.8	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB550C5-525AXSP04	-	479.3	-	412.4	794.5	-	476.7	-	410.7	787.8	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB550C5-425AXSP04	-	436.5	332.3	374.4	732.3	-	434.3	331.9	373.2	726.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB750C5-625AXSP04	-	548.4	-	473.3	901.6	-	546	-	471.9	893.3	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB750C5-525AXSP04	-	514.3	393.7	441.9	855.3	-	512.3	393.5	440.8	848.3	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB750C5-425AXSP04	-	468.2	356.5	401.5	787.6	-	466.6	356.1	400.9	782.2	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB370K8-625AXSP06	-	441	344.1	382.4	710.6	-	436.9	341.8	379.3	702.5	654	22.1	4"	523	14.6	4"	785	31	4"
EAW-VD15S4ZB370K8-525AXSP04	-	406.1	-	-	669.7	-	403.5	-	-	662.8	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB370K8-425AXSP04	-	372.8	-	320.5	622.2	-	370.7	-	319.2	616.7	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB550K8-625AXSP04	-	485.8	-	-	795	-	483	-	-	787.6	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB550K8-525AXSP04	-	456.6	-	393.2	756	-	454.2	-	391.7	748.9	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB550K8-425AXSP04	-	417.9	318.7	358.9	700.1	-	416.1	318	357.3	694.5	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S4ZB750K8-625AXSP04	-	527.8	-	455.2	866	-	525.1	-	454	858.5	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD15S4ZB750K8-525AXSP04	-	496	380.1	426.5	823	-	493.9	379.2	425.3	817	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD15S4ZB750K8-425AXSP04	-	452.6	344.5	388.5	760.4	-	451.1	344.2	387.2	755.1	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD15S5ZB370K4-625AXSP04	-	544.9	-	472.2	882.4	-	540.5	-	468.9	872.5	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB370K4-525AXSP04	-	514.2	397.4	444	842.1	-	510.2	395.4	441.1	833.4	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB370K4-425AXSP04	305.2	472.1	362.6	406.7	783.9	304.9	469.3	361.1	404.4	775.9	654	18.5	4"	523	12.2	4"	785	26	4"
EAW-VD15S5ZB550K4-625AXSP04	-	615.4	477.4	532.4	1000.5	-	610.3	474.7	528.7	990.1	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB550K4-525AXSP04	377.1	578.4	446.2	499.2	951.9	376.7	574.5	443.9	496.4	943	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB550K4-425AXSP02	-	-	-	-	842.7	-	-	-	-	837.6	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB750K4-625AXSP04	-	668	517.2	577.2	1090	-	664.4	515.9	574.9	1080.5	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB750K4-525AXSP04	407.9	627.7	483.1	541.6	1036.5	408	624.1	481.8	539.3	1027.6	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB750K4-425AXSP02	-	-	-	-	914.3	-	-	-	-	911.1	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB370K5-625AXSP04	-	544.9	-	472.2	882.4	-	540.5	-	468.9	872.5	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB370K5-525AXSP04	-	514.2	397.4	444	842.1	-	510.2	395.4	441.1	833.4	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB370K5-425AXSP04	305.2	472.1	362.6	406.7	783.9	304.9	469.3	361.1	404.4	775.9	654	18.5	4"	523	12.2	4"	785	26	4"
EAW-VD15S5ZB550K5-625AXSP04	-	615.4	477.4	532.4	1000.5	-	610.3	474.7	528.7	990.1	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB550K5-525AXSP04	377.1	578.4	446.2	499.2	951.9	376.7	574.5	443.9	496.4	943	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB550K5-425AXSP02	-	-	-	-	842.7	-	-	-	-	837.6	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB750K5-625AXSP04	-	668	517.2	577.2	1090	-	664.4	515.9	574.9	1080.5	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S5ZB750K5-525AXSP04	407.9	627.7	483.1	541.6	1036.5	408	624.1	481.8	539.3	1027.6	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB750K5-425AXSP02	-	-	-	-	914.3	-	-	-	-	911.1	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB370C4-625AXSP04	-	569.9	-	492.9	923.3	-	564.6	-	489.6	912.9	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB370C4-525AXSP04	-	536.4	414.1	462.9	880.2	-	532.2	412.1	459.9	870.1	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB370C4-425AXSP04	317.1	491.3	376.8	422.9	815.6	316.7	487.5	375.2	420.3	807.9	654	18.5	4"	523	12.2	4"	785	26	4"
EAW-VD15S5ZB550C4-625AXSP04	-	648.1	502.2	560.3	1055.8	-	642.6	499.9	556.9	1044.4	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB550C4-525AXSP04	395.2	607.3	467.2	523.7	1000.6	394.8	603	465.4	520.7	990.9	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB550C4-425AXSP02	-	-	-	-	881	-	-	-	-	875.2	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB750C4-625AXSP04	456.3	694.1	537.7	600.3	1134.9	456.1	690.2	535.3	596.8	1124.4	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB750C4-525AXSP04	422.3	650.9	501.1	561.3	1075.9	422.6	647.4	499.2	559	1067	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB750C4-425AXSP02	-	-	-	-	946.6	-	-	-	-	943.3	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB370C5-625AXSP04	-	569.9	-	492.9	923.3	-	564.6	-	489.6	912.9	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB370C5-525AXSP04	-	536.4	414.1	462.9	880.2	-	532.2	412.1	459.9	870.1	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB370C5-425AXSP04	317.1	491.3	376.8	422.9	815.6	316.7	487.5	375.2	420.3	807.9	654	18.5	4"	523	12.2	4"	785	26	4"
EAW-VD15S5ZB550C5-625AXSP04	-	648.1	502.2	560.3	1055.8	-	642.6	499.9	556.9	1044.4	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB550C5-525AXSP04	395.2	607.3	467.2	523.7	1000.6	394.8	603	465.4	520.7	990.9	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB550C5-425AXSP02	-	-	-	-	881	-	-	-	-	875.2	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB750C5-625AXSP04	456.3	694.1	537.7	600.3	1134.9	456.1	690.2	535.3	596.8	1124.4	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB750C5-525AXSP04	422.3	650.9	501.1	561.3	1075.9	422.6	647.4	499.2	559	1067	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB750C5-425AXSP02	-	-	-	-	946.6	-	-	-	-	943.3	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB370K8-625AXSP04	-	544.9	-	472.2	882.4	-	540.5	-	468.9	872.5	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB370K8-525AXSP04	-	514.2	397.4	444	842.1	-	510.2	395.4	441.1	833.4	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB370K8-425AXSP04	305.2	472.1	362.6	406.7	783.9	304.9	469.3	361.1	404.4	775.9	654	18.5	4"	523	12.2	4"	785	26	4"
EAW-VD15S5ZB550K8-625AXSP04	-	615.4	477.4	532.4	1000.5	-	610.3	474.7	528.7	990.1	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB550K8-525AXSP04	377.1	578.4	446.2	499.2	951.9	376.7	574.5	443.9	496.4	943	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB550K8-425AXSP02	-	-	-	-	842.7	-	-	-	-	837.6	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S5ZB750K8-625AXSP04	-	668	517.2	577.2	1090	-	664.4	515.9	574.9	1080.5	981	17.4	(2) 4"	785	14.2	4"	1177	24.5	(2) 4"
EAW-VD15S5ZB750K8-525AXSP04	407.9	627.7	483.1	541.6	1036.5	408	624.1	481.8	539.3	1027.6	812	19.9	4"	649	13.1	4"	974	23.8	(2) 4"
EAW-VD15S5ZB750K8-425AXSP02	-	-	-	-	914.3	-	-	-	-	911.1	1308	10.5	(2) 4"	1046	6.9	(2) 4"	1570	14.8	(2) 4"
EAW-VD15S6ZB370K4-625AXSP04	-	659.3	514.3	571.5	1063.5	-	653.1	510.8	566.8	1050.4	981	20.4	(2) 4"	785	16.2	4"	1177	28.6	(2) 4"
EAW-VD15S6ZB370K4-525AXSP02	-	-	-	-	984.2	-	-	-	-	975.5	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB370K4-425AXSP02	-	-	-	-	908.7	-	-	-	-	902.1	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB550K4-625AXSP02	-	-	-	-	1166.8	-	-	-	-	1157.6	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB550K4-525AXSP02	-	-	-	-	1110.3	-	-	-	-	1101.5	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB550K4-425AXSP02	-	-	-	-	1021.3	-	-	-	-	1015	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB750K4-625AXSP02	-	-	-	-	1270.5	-	-	-	-	1261.2	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB750K4-525AXSP02	-	-	-	-	1208.1	-	-	-	-	1199.6	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB750K4-425AXSP02	-	651.4	-	-	1108.4	-	650.7	-	-	1102.7	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB370K5-625AXSP04	-	659.3	514.3	571.5	1063.5	-	653.1	510.8	566.8	1050.4	981	20.4	(2) 4"	785	16.2	4"	1177	28.6	(2) 4"
EAW-VD15S6ZB370K5-525AXSP02	-	-	-	-	984.2	-	-	-	-	975.5	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB370K5-425AXSP02	-	-	-	-	908.7	-	-	-	-	902.1	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB550K5-625AXSP02	-	-	-	-	1166.8	-	-	-	-	1157.6	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB550K5-525AXSP02	-	-	-	-	1110.3	-	-	-	-	1101.5	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB550K5-425AXSP02	-	-	-	-	1021.3	-	-	-	-	1015	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB750K5-625AXSP02	-	-	-	-	1270.5	-	-	-	-	1261.2	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB750K5-525AXSP02	-	-	-	-	1208.1	-	-	-	-	1199.6	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB750K5-425AXSP02	-	651.4	-	-	1108.4	-	650.7	-	-	1102.7	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB370C4-625AXSP04	459.2	688.7	536.8	597.4	1112.9	457.6	682.3	533.2	592.6	1099.1	981	20.4	(2) 4"	785	16.2	4"	1177	28.6	(2) 4"
EAW-VD15S6ZB370C4-525AXSP02	-	-	-	-	1027.3	-	-	-	-	1018.2	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB370C4-425AXSP02	-	-	-	-	946.2	-	-	-	-	939.1	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB550C4-625AXSP02	-	-	-	-	1230.9	-	-	-	-	1220.7	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB550C4-525AXSP02	-	-	-	-	1166.6	-	-	-	-	1157	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB550C4-425AXSP02	-	627.6	-	-	1067.9	-	626.9	-	-	1060.7	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB750C4-625AXSP02	-	-	-	-	1320.9	-	-	-	-	1312.1	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB750C4-525AXSP02	-	-	-	-	1253.6	-	-	-	-	1246.9	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB750C4-425AXSP02	-	673.4	-	-	1147.7	-	673.9	-	-	1141.8	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB370C5-625AXSP04	459.2	688.7	536.8	597.4	1112.9	457.6	682.3	533.2	592.6	1099.1	981	20.4	(2) 4"	785	16.2	4"	1177	28.6	(2) 4"
EAW-VD15S6ZB370C5-525AXSP02	-	-	-	-	1027.3	-	-	-	-	1018.2	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB370C5-425AXSP02	-	-	-	-	946.2	-	-	-	-	939.1	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB550C5-625AXSP02	-	-	-	-	1230.9	-	-	-	-	1220.7	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB550C5-525AXSP02	-	-	-	-	1166.6	-	-	-	-	1157	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB550C5-425AXSP02	-	627.6	-	-	1067.9	-	626.9	-	-	1060.7	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB750C5-625AXSP02	-	-	-	-	1320.9	-	-	-	-	1312.1	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB750C5-525AXSP02	-	-	-	-	1253.6	-	-	-	-	1246.9	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB750C5-425AXSP02	-	673.4	-	-	1147.7	-	673.9	-	-	1141.8	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB370K8-625AXSP04	-	659.3	514.3	571.5	1063.5	-	653.1	510.8	566.8	1050.4	981	20.4	(2) 4"	785	16.2	4"	1177	28.6	(2) 4"
EAW-VD15S6ZB370K8-525AXSP02	-	-	-	-	984.2	-	-	-	-	975.5	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB370K8-425AXSP02	-	-	-	-	908.7	-	-	-	-	902.1	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB550K8-625AXSP02	-	-	-	-	1166.8	-	-	-	-	1157.6	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB550K8-525AXSP02	-	-	-	-	1110.3	-	-	-	-	1101.5	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB550K8-425AXSP02	-	-	-	-	1021.3	-	-	-	-	1015	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S6ZB750K8-625AXSP02	-	-	-	-	1270.5	-	-	-	-	1261.2	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD15S6ZB750K8-525AXSP02	-	-	-	-	1208.1	-	-	-	-	1199.6	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD15S6ZB750K8-425AXSP02	-	651.4	-	-	1108.4	-	650.7	-	-	1102.7	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD15S1ZK370K4-625AXSP16	-	113.4	-	-	183.3	-	112.4	-	-	181.1	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK370K4-525AXSP16	-	105.5	-	91	172.9	-	104.6	-	90.4	171	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK370K4-425AXSP16	-	97	74.5	83.5	161.3	-	96.4	74.1	83.1	159.7	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK550K4-625AXSP16	-	128.5	-	-	208.7	-	127.4	-	-	206.3	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK550K4-525AXSP16	-	118.9	91.5	102.5	195.9	-	118	91.2	102	193.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK550K4-425AXSP16	-	109.1	83.4	93.8	181.9	-	108.4	83.1	93.3	180.1	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK750K4-625AXSP16	-	139.9	-	121	228.4	-	139.1	-	120.3	226	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK750K4-525AXSP16	-	129.4	99.4	111.5	213.9	-	128.5	99.1	110.9	211.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK750K4-425AXSP12	-	118.3	-	101.6	199.6	-	118	-	101.3	198	218	17.7	2"	174	11.7	2"	262	19.7	3"
EAW-VD15S1ZK370K5-625AXSP16	-	113.4	-	-	183.3	-	112.4	-	-	181.1	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK370K5-525AXSP16	-	105.5	-	91	172.9	-	104.6	-	90.4	171	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK370K5-425AXSP16	-	97	74.5	83.5	161.3	-	96.4	74.1	83.1	159.7	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK550K5-625AXSP16	-	128.5	-	-	208.7	-	127.4	-	-	206.3	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK550K5-525AXSP16	-	118.9	91.5	102.5	195.9	-	118	91.2	102	193.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK550K5-425AXSP16	-	109.1	83.4	93.8	181.9	-	108.4	83.1	93.3	180.1	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK750K5-625AXSP16	-	139.9	-	121	228.4	-	139.1	-	120.3	226	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK750K5-525AXSP16	-	129.4	99.4	111.5	213.9	-	128.5	99.1	110.9	211.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK750K5-425AXSP12	-	118.3	-	101.6	199.6	-	118	-	101.3	198	218	17.7	2"	174	11.7	2"	262	19.7	3"
EAW-VD15S1ZK370C4-625AXSP16	-	118.4	-	-	192	-	117.5	-	-	189.6	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK370C4-525AXSP16	-	110	-	94.8	180.6	-	109	-	94.2	178.6	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK370C4-425AXSP16	-	100.8	77.3	86.7	167.7	-	100.1	76.9	86.2	166	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK550C4-625AXSP16	-	135.1	-	116.7	219.8	-	133.9	-	116	217.5	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK550C4-525AXSP16	-	124.5	95.8	107.3	205.7	-	123.7	95.3	106.7	203.5	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK550C4-425AXSP16	72.9	113.7	86.9	97.6	189.8	72.8	113	86.5	97.2	188	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK750C4-625AXSP16	-	145.5	112.5	125.7	237.6	-	144.5	112.2	125	235.2	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK750C4-525AXSP16	-	134.1	103	115.5	222	-	133.4	102.6	115.1	220.1	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK750C4-425AXSP12	-	122.5	-	104.9	206.5	-	122.1	-	104.7	205.1	218	17.7	2"	174	11.7	2"	262	19.7	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1ZK370C5-625AXSP16	-	118.4	-	-	192	-	117.5	-	-	189.6	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK370C5-525AXSP16	-	110	-	94.8	180.6	-	109	-	94.2	178.6	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK370C5-425AXSP16	-	100.8	77.3	86.7	167.7	-	100.1	76.9	86.2	166	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK550C5-625AXSP16	-	135.1	-	116.7	219.8	-	133.9	-	116	217.5	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK550C5-525AXSP16	-	124.5	95.8	107.3	205.7	-	123.7	95.3	106.7	203.5	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK550C5-425AXSP16	72.9	113.7	86.9	97.6	189.8	72.8	113	86.5	97.2	188	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK750C5-625AXSP16	-	145.5	112.5	125.7	237.6	-	144.5	112.2	125	235.2	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK750C5-525AXSP16	-	134.1	103	115.5	222	-	133.4	102.6	115.1	220.1	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK750C5-425AXSP12	-	122.5	-	104.9	206.5	-	122.1	-	104.7	205.1	218	17.7	2"	174	11.7	2"	262	19.7	3"
EAW-VD15S1ZK370K8-625AXSP16	-	113.4	-	-	183.3	-	112.4	-	-	181.1	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK370K8-525AXSP16	-	105.5	-	91	172.9	-	104.6	-	90.4	171	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK370K8-425AXSP16	-	97	74.5	83.5	161.3	-	96.4	74.1	83.1	159.7	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK550K8-625AXSP16	-	128.5	-	-	208.7	-	127.4	-	-	206.3	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK550K8-525AXSP16	-	118.9	91.5	102.5	195.9	-	118	91.2	102	193.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK550K8-425AXSP16	-	109.1	83.4	93.8	181.9	-	108.4	83.1	93.3	180.1	157	20	2"	126	16	1-1/2"	189	28.1	2"
EAW-VD15S1ZK750K8-625AXSP16	-	139.9	-	121	228.4	-	139.1	-	120.3	226	242	18.7	3"	194	15.3	2"	291	26.2	3"
EAW-VD15S1ZK750K8-525AXSP16	-	129.4	99.4	111.5	213.9	-	128.5	99.1	110.9	211.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1ZK750K8-425AXSP12	-	118.3	-	101.6	199.6	-	118	-	101.3	198	218	17.7	2"	174	11.7	2"	262	19.7	3"
EAW-VD15S2ZK370K4-625AXSP08	-	226	-	-	365.8	-	224.3	-	-	361.4	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK370K4-525AXSP08	-	213.1	-	-	349.1	-	211.5	-	-	345.2	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK370K4-425AXSP08	-	197.4	151.3	169.8	327.1	-	195.8	-	168.9	323.9	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK550K4-625AXSP08	-	256	-	-	416.4	-	253.9	-	-	411.7	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK550K4-525AXSP08	-	240.3	185.1	207.3	395.7	-	238.8	-	206.2	391.6	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK550K4-425AXSP08	-	221.8	169.8	190.6	369.3	-	220.5	169.1	189.8	365.9	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK750K4-625AXSP08	-	279.2	-	241.4	455.3	-	277.2	-	240	451	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK750K4-525AXSP08	-	261.6	201.3	225.6	432.1	-	260.2	200.5	224.4	428	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK750K4-425AXSP08	154.3	241	184.2	207.1	402.4	154.4	239.5	183.7	206.4	399.2	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK370K5-625AXSP08	-	226	-	-	365.8	-	224.3	-	-	361.4	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK370K5-525AXSP08	-	213.1	-	-	349.1	-	211.5	-	-	345.2	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK370K5-425AXSP08	-	197.4	151.3	169.8	327.1	-	195.8	-	168.9	323.9	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK550K5-625AXSP08	-	256	-	-	416.4	-	253.9	-	-	411.7	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK550K5-525AXSP08	-	240.3	185.1	207.3	395.7	-	238.8	-	206.2	391.6	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK550K5-425AXSP08	-	221.8	169.8	190.6	369.3	-	220.5	169.1	189.8	365.9	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK750K5-625AXSP08	-	279.2	-	241.4	455.3	-	277.2	-	240	451	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK750K5-525AXSP08	-	261.6	201.3	225.6	432.1	-	260.2	200.5	224.4	428	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK750K5-425AXSP08	154.3	241	184.2	207.1	402.4	154.4	239.5	183.7	206.4	399.2	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK370C4-625AXSP08	-	236.3	-	-	383.1	-	234.2	-	-	378.5	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK370C4-525AXSP08	-	222.2	-	191.6	364.7	-	220.4	-	190.4	360.5	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK370C4-425AXSP08	-	204.8	157.2	176.3	340.2	-	203.3	156.4	175.3	336.7	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK550C4-625AXSP08	-	269.5	-	232.8	438.7	-	267.2	-	231.5	434.1	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK550C4-525AXSP08	-	251.8	193.9	217.2	415.5	-	250	192.9	215.7	410.9	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK550C4-425AXSP08	-	231.1	176.9	198.7	385.8	-	229.6	176.1	197.8	382.1	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK750C4-625AXSP08	-	290.3	224.4	250.5	474.2	-	288.3	-	249.4	469.3	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK750C4-525AXSP08	-	271.6	208.7	233.7	449	-	269.7	208	232.8	444.7	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK750C4-425AXSP08	159.5	249.2	190.5	214.2	417.1	159.5	247.9	189.9	213.1	413	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK370C5-625AXSP08	-	236.3	-	-	383.1	-	234.2	-	-	378.5	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK370C5-525AXSP08	-	222.2	-	191.6	364.7	-	220.4	-	190.4	360.5	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK370C5-425AXSP08	-	204.8	157.2	176.3	340.2	-	203.3	156.4	175.3	336.7	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK550C5-625AXSP08	-	269.5	-	232.8	438.7	-	267.2	-	231.5	434.1	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK550C5-525AXSP08	-	251.8	193.9	217.2	415.5	-	250	192.9	215.7	410.9	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK550C5-425AXSP08	-	231.1	176.9	198.7	385.8	-	229.6	176.1	197.8	382.1	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK750C5-625AXSP08	-	290.3	224.4	250.5	474.2	-	288.3	-	249.4	469.3	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK750C5-525AXSP08	-	271.6	208.7	233.7	449	-	269.7	208	232.8	444.7	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK750C5-425AXSP08	159.5	249.2	190.5	214.2	417.1	159.5	247.9	189.9	213.1	413	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK370K8-625AXSP08	-	226	-	-	365.8	-	224.3	-	-	361.4	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK370K8-525AXSP08	-	213.1	-	-	349.1	-	211.5	-	-	345.2	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK370K8-425AXSP08	-	197.4	151.3	169.8	327.1	-	195.8	-	168.9	323.9	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK550K8-625AXSP08	-	256	-	-	416.4	-	253.9	-	-	411.7	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK550K8-525AXSP08	-	240.3	185.1	207.3	395.7	-	238.8	-	206.2	391.6	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK550K8-425AXSP08	-	221.8	169.8	190.6	369.3	-	220.5	169.1	189.8	365.9	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S2ZK750K8-625AXSP08	-	279.2	-	241.4	455.3	-	277.2	-	240	451	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD15S2ZK750K8-525AXSP08	-	261.6	201.3	225.6	432.1	-	260.2	200.5	224.4	428	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD15S2ZK750K8-425AXSP08	154.3	241	184.2	207.1	402.4	154.4	239.5	183.7	206.4	399.2	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD15S3ZK370K4-625AXSP06	-	342.2	-	-	551.7	-	338.7	-	-	545	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK370K4-525AXSP06	-	324	-	280.2	529.1	-	321.1	-	278.1	523.1	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK370K4-425AXSP06	-	296.9	228.3	255.8	491.3	-	294.9	227.1	254.4	486.4	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK550K4-625AXSP06	-	387.6	-	335.3	628.1	-	384	-	333	620.9	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK550K4-525AXSP06	-	365.7	282.4	316	599.9	-	363.2	281	313.9	593.7	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK550K4-425AXSP06	215.6	334.1	256.3	287.6	554.6	215.5	331.7	254.9	286	549.6	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK750K4-625AXSP06	-	422.9	328	365.4	687.6	-	419.3	326.1	363.2	680.4	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK750K4-525AXSP06	260	398.7	307.2	343.6	655.3	259.7	395.9	306	341.7	649	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK750K4-425AXSP04	-	351.2	-	-	592.9	-	350.3	-	-	588.3	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S3ZK370K5-625AXSP06	-	342.2	-	-	551.7	-	338.7	-	-	545	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK370K5-525AXSP06	-	324	-	280.2	529.1	-	321.1	-	278.1	523.1	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK370K5-425AXSP06	-	296.9	228.3	255.8	491.3	-	294.9	227.1	254.4	486.4	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK550K5-625AXSP06	-	387.6	-	335.3	628.1	-	384	-	333	620.9	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK550K5-525AXSP06	-	365.7	282.4	316	599.9	-	363.2	281	313.9	593.7	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK550K5-425AXSP06	215.6	334.1	256.3	287.6	554.6	215.5	331.7	254.9	286	549.6	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK750K5-625AXSP06	-	422.9	328	365.4	687.6	-	419.3	326.1	363.2	680.4	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK750K5-525AXSP06	260	398.7	307.2	343.6	655.3	259.7	395.9	306	341.7	649	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK750K5-425AXSP04	-	351.2	-	-	592.9	-	350.3	-	-	588.3	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S3ZK370C4-625AXSP06	-	357.4	-	309.8	577.8	-	354.2	-	307.4	570.8	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK370C4-525AXSP06	-	337.9	261.5	292	552.9	-	334.8	259.8	289.7	545.8	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK370C4-425AXSP06	-	308.5	237.3	265.6	511	-	306.3	235.6	264.1	505.7	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK550C4-625AXSP06	-	407.6	316.4	352.8	661.7	-	404.2	314.6	350.3	654.7	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK550C4-525AXSP06	-	383.6	295.9	330.9	630	-	380.4	294.3	328.5	623	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK550C4-425AXSP04	-	336.9	-	-	567.8	-	335.4	-	-	563.3	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S3ZK750C4-625AXSP06	-	439.1	340.3	379.6	715.4	-	436.1	338.8	377.5	708	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK750C4-525AXSP06	269.2	413.4	318.7	356.6	681	268.9	410.5	316.9	354.6	674.4	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK750C4-425AXSP04	-	363	-	311	613.6	-	361.9	-	310.6	609.4	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S3ZK370C5-625AXSP06	-	357.4	-	309.8	577.8	-	354.2	-	307.4	570.8	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK370C5-525AXSP06	-	337.9	261.5	292	552.9	-	334.8	259.8	289.7	545.8	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK370C5-425AXSP06	-	308.5	237.3	265.6	511	-	306.3	235.6	264.1	505.7	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK550C5-625AXSP06	-	407.6	316.4	352.8	661.7	-	404.2	314.6	350.3	654.7	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK550C5-525AXSP06	-	383.6	295.9	330.9	630	-	380.4	294.3	328.5	623	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK550C5-425AXSP04	-	336.9	-	-	567.8	-	335.4	-	-	563.3	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S3ZK750C5-625AXSP06	-	439.1	340.3	379.6	715.4	-	436.1	338.8	377.5	708	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK750C5-525AXSP06	269.2	413.4	318.7	356.6	681	268.9	410.5	316.9	354.6	674.4	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK750C5-425AXSP04	-	363	-	311	613.6	-	361.9	-	310.6	609.4	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S3ZK370K8-625AXSP06	-	342.2	-	-	551.7	-	338.7	-	-	545	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK370K8-525AXSP06	-	324	-	280.2	529.1	-	321.1	-	278.1	523.1	545	18.3	4"	436	14.4	3"	654	25.7	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3ZK370K8-425AXSP06	-	296.9	228.3	255.8	491.3	-	294.9	227.1	254.4	486.4	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK550K8-625AXSP06	-	387.6	-	335.3	628.1	-	384	-	333	620.9	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK550K8-525AXSP06	-	365.7	282.4	316	599.9	-	363.2	281	313.9	593.7	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK550K8-425AXSP06	215.6	334.1	256.3	287.6	554.6	215.5	331.7	254.9	286	549.6	436	20	3"	349	13.2	3"	523	24.8	4"
EAW-VD15S3ZK750K8-625AXSP06	-	422.9	328	365.4	687.6	-	419.3	326.1	363.2	680.4	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD15S3ZK750K8-525AXSP06	260	398.7	307.2	343.6	655.3	259.7	395.9	306	341.7	649	545	18.3	4"	436	14.4	3"	654	25.7	4"
EAW-VD15S3ZK750K8-425AXSP04	-	351.2	-	-	592.9	-	350.3	-	-	588.3	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD15S4ZK370K4-625AXSP04	-	-	-	-	731.6	-	-	-	-	722.8	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK370K4-525AXSP04	-	426.1	-	-	698.9	-	422.9	-	-	691.1	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK370K4-425AXSP04	-	391.5	-	337.1	650.1	-	388.8	-	334.8	643.7	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK550K4-625AXSP04	-	511.4	-	-	831.9	-	507.3	-	-	822.4	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK550K4-525AXSP04	-	480.7	-	414.5	791.3	-	477.5	-	412.4	784.1	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK550K4-425AXSP04	-	440.3	336.8	378.2	733.6	-	437.2	335.6	376.7	727.1	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK750K4-625AXSP04	-	557.7	-	482.2	910.6	-	553.8	-	479.4	901.1	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK750K4-525AXSP04	-	523.2	402.5	451.2	865.2	-	520.3	401	448.7	857	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK750K4-425AXSP04	305.9	477.7	365.4	410.8	799.4	306.2	475.6	364.5	409	793	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK370K5-625AXSP04	-	-	-	-	731.6	-	-	-	-	722.8	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK370K5-525AXSP04	-	426.1	-	-	698.9	-	422.9	-	-	691.1	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK370K5-425AXSP04	-	391.5	-	337.1	650.1	-	388.8	-	334.8	643.7	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK550K5-625AXSP04	-	511.4	-	-	831.9	-	507.3	-	-	822.4	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK550K5-525AXSP04	-	480.7	-	414.5	791.3	-	477.5	-	412.4	784.1	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK550K5-425AXSP04	-	440.3	336.8	378.2	733.6	-	437.2	335.6	376.7	727.1	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK750K5-625AXSP04	-	557.7	-	482.2	910.6	-	553.8	-	479.4	901.1	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK750K5-525AXSP04	-	523.2	402.5	451.2	865.2	-	520.3	401	448.7	857	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK750K5-425AXSP04	305.9	477.7	365.4	410.8	799.4	306.2	475.6	364.5	409	793	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK370C4-625AXSP04	-	472.1	-	-	765.4	-	467.9	-	-	756.9	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK370C4-525AXSP04	-	444.3	-	383.2	729.4	-	440.8	-	380.7	721	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK370C4-425AXSP04	-	406.7	311.5	349.9	676	-	403.8	310.3	348	669.1	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK550C4-625AXSP04	-	538.3	-	465.1	877.4	-	533.9	-	462.4	867.1	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK550C4-525AXSP04	-	503.5	387.8	434.5	830.9	-	500	385.8	431.5	821.8	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK550C4-425AXSP04	-	458.7	350.9	394.2	766.4	-	455.9	349.5	392.5	758.2	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK750C4-625AXSP04	-	579.8	-	500.3	947.3	-	575.9	-	498.2	938.7	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK750C4-525AXSP04	-	543.2	416.8	467.4	897.9	-	539.4	415.9	465.5	889.3	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK750C4-425AXSP04	316.2	494.5	377.2	424.3	827.3	316.4	491.4	376.1	422.9	820.4	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK370C5-625AXSP04	-	472.1	-	-	765.4	-	467.9	-	-	756.9	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK370C5-525AXSP04	-	444.3	-	383.2	729.4	-	440.8	-	380.7	721	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK370C5-425AXSP04	-	406.7	311.5	349.9	676	-	403.8	310.3	348	669.1	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK550C5-625AXSP04	-	538.3	-	465.1	877.4	-	533.9	-	462.4	867.1	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK550C5-525AXSP04	-	503.5	387.8	434.5	830.9	-	500	385.8	431.5	821.8	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK550C5-425AXSP04	-	458.7	350.9	394.2	766.4	-	455.9	349.5	392.5	758.2	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK750C5-625AXSP04	-	579.8	-	500.3	947.3	-	575.9	-	498.2	938.7	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK750C5-525AXSP04	-	543.2	416.8	467.4	897.9	-	539.4	415.9	465.5	889.3	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK750C5-425AXSP04	316.2	494.5	377.2	424.3	827.3	316.4	491.4	376.1	422.9	820.4	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK370K8-625AXSP04	-	-	-	-	731.6	-	-	-	-	722.8	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK370K8-525AXSP04	-	426.1	-	-	698.9	-	422.9	-	-	691.1	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK370K8-425AXSP04	-	391.5	-	337.1	650.1	-	388.8	-	334.8	643.7	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK550K8-625AXSP04	-	511.4	-	-	831.9	-	507.3	-	-	822.4	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK550K8-525AXSP04	-	480.7	-	414.5	791.3	-	477.5	-	412.4	784.1	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK550K8-425AXSP04	-	440.3	336.8	378.2	733.6	-	437.2	335.6	376.7	727.1	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S4ZK750K8-625AXSP04	-	557.7	-	482.2	910.6	-	553.8	-	479.4	901.1	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD15S4ZK750K8-525AXSP04	-	523.2	402.5	451.2	865.2	-	520.3	401	448.7	857	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD15S4ZK750K8-425AXSP04	305.9	477.7	365.4	410.8	799.4	306.2	475.6	364.5	409	793	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD15S5ZK370K4-625AXSP04	-	571	-	494.7	919.5	-	565.2	-	490.8	907.4	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK370K4-525AXSP04	-	538.7	417.8	465.8	878.8	-	533.9	414.7	462.2	867.9	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK370K4-425AXSP02	-	-	-	-	785.4	-	-	-	-	780	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK550K4-625AXSP04	-	646.1	502.6	559.5	1045.6	-	640.8	499.9	555.7	1033.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK550K4-525AXSP04	399.1	607.9	470	525.3	996.3	397.6	603.1	467.6	521.8	984.8	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK550K4-425AXSP02	-	-	-	-	885.2	-	-	-	-	878.9	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK750K4-625AXSP04	466.8	704.8	547.4	610.5	1144.7	465.7	699.7	544.2	606.1	1132.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK750K4-525AXSP02	-	-	-	-	1049.6	-	-	-	-	1042.6	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK750K4-425AXSP02	-	-	-	-	963.5	-	-	-	-	957.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK370K5-625AXSP04	-	571	-	494.7	919.5	-	565.2	-	490.8	907.4	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK370K5-525AXSP04	-	538.7	417.8	465.8	878.8	-	533.9	414.7	462.2	867.9	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK370K5-425AXSP02	-	-	-	-	785.4	-	-	-	-	780	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK550K5-625AXSP04	-	646.1	502.6	559.5	1045.6	-	640.8	499.9	555.7	1033.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK550K5-525AXSP04	399.1	607.9	470	525.3	996.3	397.6	603.1	467.6	521.8	984.8	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK550K5-425AXSP02	-	-	-	-	885.2	-	-	-	-	878.9	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK750K5-625AXSP04	466.8	704.8	547.4	610.5	1144.7	465.7	699.7	544.2	606.1	1132.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK750K5-525AXSP02	-	-	-	-	1049.6	-	-	-	-	1042.6	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK750K5-425AXSP02	-	-	-	-	963.5	-	-	-	-	957.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK370C4-625AXSP04	-	596.3	464.7	517	962	-	590.9	461.7	512.9	950.3	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK370C4-525AXSP04	-	561.8	435.2	485.5	917.1	-	556.6	431.9	481.6	906.5	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK370C4-425AXSP02	-	-	-	-	816.4	-	-	-	-	810.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK550C4-625AXSP04	-	680.2	528.7	588.7	1102.9	-	673.7	525	584.5	1090	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK550C4-525AXSP02	-	-	-	-	1009.5	-	-	-	-	1001.2	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK550C4-425AXSP02	-	-	-	-	924.3	-	-	-	-	917.3	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK750C4-625AXSP04	484.8	732.8	568.6	633.6	1190.9	483.3	726.8	565.5	630	1178.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK750C4-525AXSP02	-	-	-	-	1090.3	-	-	-	-	1082.9	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK750C4-425AXSP02	-	-	-	-	998.1	-	-	-	-	991.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK370C5-625AXSP04	-	596.3	464.7	517	962	-	590.9	461.7	512.9	950.3	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK370C5-525AXSP04	-	561.8	435.2	485.5	917.1	-	556.6	431.9	481.6	906.5	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK370C5-425AXSP02	-	-	-	-	816.4	-	-	-	-	810.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK550C5-625AXSP04	-	680.2	528.7	588.7	1102.9	-	673.7	525	584.5	1090	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK550C5-525AXSP02	-	-	-	-	1009.5	-	-	-	-	1001.2	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK550C5-425AXSP02	-	-	-	-	924.3	-	-	-	-	917.3	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK750C5-625AXSP04	484.8	732.8	568.6	633.6	1190.9	483.3	726.8	565.5	630	1178.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK750C5-525AXSP02	-	-	-	-	1090.3	-	-	-	-	1082.9	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK750C5-425AXSP02	-	-	-	-	998.1	-	-	-	-	991.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S6ZK370K8-625AXSP04	-	571	-	494.7	919.5	-	565.2	-	490.8	907.4	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK370K8-525AXSP04	-	538.7	417.8	465.8	878.8	-	533.9	414.7	462.2	867.9	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK370K8-425AXSP02	-	-	-	-	785.4	-	-	-	-	780	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK550K8-625AXSP04	-	646.1	502.6	559.5	1045.6	-	640.8	499.9	555.7	1033.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK550K8-525AXSP04	399.1	607.9	470	525.3	996.3	397.6	603.1	467.6	521.8	984.8	812	21.6	4"	649	14.2	4"	974	26.1	(2) 4"
EAW-VD15S5ZK550K8-425AXSP02	-	-	-	-	885.2	-	-	-	-	878.9	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S5ZK750K8-625AXSP04	466.8	704.8	547.4	610.5	1144.7	465.7	699.7	544.2	606.1	1132.7	981	19.1	(2) 4"	785	15.3	4"	1177	26.8	(2) 4"
EAW-VD15S5ZK750K8-525AXSP02	-	-	-	-	1049.6	-	-	-	-	1042.6	1635	12.8	(2) 4"	1308	8.4	(2) 4"	1962	14.9	(3) 4"
EAW-VD15S5ZK750K8-425AXSP02	-	-	-	-	963.5	-	-	-	-	957.6	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD15S6ZK370K4-625AXSP04	463.6	689.9	539.6	598.6	1107	460.3	682.8	534.7	593.1	1093.5	981	22.4	(2) 4"	785	17.5	4"	1177	31.4	(2) 4"
EAW-VD15S6ZK370K4-525AXSP02	-	-	-	-	1028.8	-	-	-	-	1018.7	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK370K4-425AXSP02	-	-	-	-	951.2	-	-	-	-	943.4	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK550K4-625AXSP02	-	-	-	-	1224.1	-	-	-	-	1211.8	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6ZK550K4-525AXSP02	-	-	-	-	1164.1	-	-	-	-	1153.7	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK550K4-425AXSP02	-	636.3	-	-	1072.5	-	634	-	-	1063.3	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK750K4-625AXSP02	-	-	-	-	1338	-	-	-	-	1325.7	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK750K4-525AXSP02	-	760.6	-	-	1270.7	-	758.9	-	-	1260.5	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK750K4-425AXSP02	-	690.6	-	-	1167.7	-	688.9	-	-	1158.8	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK370K5-625AXSP04	463.6	689.9	539.6	598.6	1107	460.3	682.8	534.7	593.1	1093.5	981	22.4	(2) 4"	785	17.5	4"	1177	31.4	(2) 4"
EAW-VD15S6ZK370K5-525AXSP02	-	-	-	-	1028.8	-	-	-	-	1018.7	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK370K5-425AXSP02	-	-	-	-	951.2	-	-	-	-	943.4	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK550K5-625AXSP02	-	-	-	-	1224.1	-	-	-	-	1211.8	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK550K5-525AXSP02	-	-	-	-	1164.1	-	-	-	-	1153.7	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK550K5-425AXSP02	-	636.3	-	-	1072.5	-	634	-	-	1063.3	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK750K5-625AXSP02	-	-	-	-	1338	-	-	-	-	1325.7	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK750K5-525AXSP02	-	760.6	-	-	1270.7	-	758.9	-	-	1260.5	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK750K5-425AXSP02	-	690.6	-	-	1167.7	-	688.9	-	-	1158.8	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK370C4-625AXSP02	-	-	-	-	1126.6	-	-	-	-	1115.6	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK370C4-525AXSP02	-	-	-	-	1073.5	-	-	-	-	1062.5	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK370C4-425AXSP02	-	-	-	-	988.9	-	-	-	-	980.5	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK550C4-625AXSP02	-	-	-	-	1289.4	-	-	-	-	1276	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK550C4-525AXSP02	-	-	-	-	1222.1	-	-	-	-	1210.3	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK550C4-425AXSP02	-	662.5	-	-	1120.1	-	659.9	-	-	1109.8	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK750C4-625AXSP02	-	-	-	-	1391.6	-	-	-	-	1380.8	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK750C4-525AXSP02	-	789.4	-	-	1320.1	-	786.5	-	-	1309.3	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK750C4-425AXSP02	-	713.4	-	610.5	1208.1	-	711.5	-	610	1200.1	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK370C5-625AXSP02	-	-	-	-	1126.6	-	-	-	-	1115.6	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK370C5-525AXSP02	-	-	-	-	1073.5	-	-	-	-	1062.5	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK370C5-425AXSP02	-	-	-	-	988.9	-	-	-	-	980.5	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK550C5-625AXSP02	-	-	-	-	1289.4	-	-	-	-	1276	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK550C5-525AXSP02	-	-	-	-	1222.1	-	-	-	-	1210.3	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK550C5-425AXSP02	-	662.5	-	-	1120.1	-	659.9	-	-	1109.8	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK750C5-625AXSP02	-	-	-	-	1391.6	-	-	-	-	1380.8	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK750C5-525AXSP02	-	789.4	-	-	1320.1	-	786.5	-	-	1309.3	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK750C5-425AXSP02	-	713.4	-	610.5	1208.1	-	711.5	-	610	1200.1	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK370K8-625AXSP04	463.6	689.9	539.6	598.6	1107	460.3	682.8	534.7	593.1	1093.5	981	22.4	(2) 4"	785	17.5	4"	1177	31.4	(2) 4"
EAW-VD15S6ZK370K8-525AXSP02	-	-	-	-	1028.8	-	-	-	-	1018.7	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK370K8-425AXSP02	-	-	-	-	951.2	-	-	-	-	943.4	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK550K8-625AXSP02	-	-	-	-	1224.1	-	-	-	-	1211.8	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK550K8-525AXSP02	-	-	-	-	1164.1	-	-	-	-	1153.7	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK550K8-425AXSP02	-	636.3	-	-	1072.5	-	634	-	-	1063.3	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S6ZK750K8-625AXSP02	-	-	-	-	1338	-	-	-	-	1325.7	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD15S6ZK750K8-525AXSP02	-	760.6	-	-	1270.7	-	758.9	-	-	1260.5	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD15S6ZK750K8-425AXSP02	-	690.6	-	-	1167.7	-	688.9	-	-	1158.8	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD15S1PB370K4-625AXSP16	-	94.6	-	-	154.6	-	94.1	-	-	153.3	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB370K4-525AXSP16	-	88	67.5	75.7	146	-	87.7	67.5	75.6	145	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB370K4-425AXSP16	-	82.4	62.8	70.7	138.1	-	82.2	62.9	70.7	137.1	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB550K4-625AXSP16	-	105.5	-	91	173.3	-	105.2	-	90.9	172.1	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB550K4-525AXSP16	-	97.8	74.9	84.1	163	-	97.7	74.9	84.1	162	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB550K4-425AXSP16	58	91.4	69.6	78.5	153.8	58.3	91.3	69.7	78.4	153.2	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB750K4-625AXSP16	-	113.2	87.2	97.6	186.6	-	113.1	87.3	97.6	185.7	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB750K4-525AXSP16	-	105	80.3	90.3	175.3	67.6	104.9	80.5	90.3	174.5	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB750K4-425AXSP12	-	94.3	-	80.6	161	-	94.4	-	80.9	160.6	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S1PB370K5-625AXSP16	-	94.6	-	-	154.6	-	94.1	-	-	153.3	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB370K5-525AXSP16	-	88	67.5	75.7	146	-	87.7	67.5	75.6	145	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB370K5-425AXSP16	-	82.4	62.8	70.7	138.1	-	82.2	62.9	70.7	137.1	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB550K5-625AXSP16	-	105.5	-	91	173.3	-	105.2	-	90.9	172.1	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB550K5-525AXSP16	-	97.8	74.9	84.1	163	-	97.7	74.9	84.1	162	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB550K5-425AXSP16	58	91.4	69.6	78.5	153.8	58.3	91.3	69.7	78.4	153.2	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB750K5-625AXSP16	-	113.2	87.2	97.6	186.6	-	113.1	87.3	97.6	185.7	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB750K5-525AXSP16	-	105	80.3	90.3	175.3	67.6	104.9	80.5	90.3	174.5	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB750K5-425AXSP12	-	94.3	-	80.6	161	-	94.4	-	80.9	160.6	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S1PB370C4-625AXSP16	-	98.3	-	84.9	161.1	-	98	-	84.8	159.9	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB370C4-525AXSP16	-	91.6	70.2	78.8	152.1	-	91.2	70.2	78.6	151	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB370C4-425AXSP16	-	85.6	65.3	73.4	143.7	-	85.3	65.3	73.4	142.8	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB550C4-625AXSP16	-	111.3	85.7	95.9	183.2	-	111	85.7	95.8	181.9	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB550C4-525AXSP16	-	102.9	78.7	88.5	171.7	-	102.8	78.8	88.4	170.9	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB550C4-425AXSP12	-	92.1	-	78.7	156.9	-	92.1	-	78.8	156.5	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S1PB750C4-625AXSP16	-	117.3	90.2	101	193.5	-	117.2	90.5	101.1	192.6	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB750C4-525AXSP16	69.5	108.8	83.1	93.4	181.9	69.9	108.8	83.3	93.5	181.2	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB750C4-425AXSP12	-	97.6	73.5	83.3	166.7	-	97.7	74	83.6	166.2	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S1PB370C5-625AXSP16	-	98.3	-	84.9	161.1	-	98	-	84.8	159.9	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB370C5-525AXSP16	-	91.6	70.2	78.8	152.1	-	91.2	70.2	78.6	151	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB370C5-425AXSP16	-	85.6	65.3	73.4	143.7	-	85.3	65.3	73.4	142.8	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB550C5-625AXSP16	-	111.3	85.7	95.9	183.2	-	111	85.7	95.8	181.9	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB550C5-525AXSP16	-	102.9	78.7	88.5	171.7	-	102.8	78.8	88.4	170.9	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB550C5-425AXSP12	-	92.1	-	78.7	156.9	-	92.1	-	78.8	156.5	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S1PB750C5-625AXSP16	-	117.3	90.2	101	193.5	-	117.2	90.5	101.1	192.6	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB750C5-525AXSP16	69.5	108.8	83.1	93.4	181.9	69.9	108.8	83.3	93.5	181.2	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB750C5-425AXSP12	-	97.6	73.5	83.3	166.7	-	97.7	74	83.6	166.2	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S1PB370K8-625AXSP16	-	94.6	-	-	154.6	-	94.1	-	-	153.3	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB370K8-525AXSP16	-	88	67.5	75.7	146	-	87.7	67.5	75.6	145	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB370K8-425AXSP16	-	82.4	62.8	70.7	138.1	-	82.2	62.9	70.7	137.1	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB550K8-625AXSP16	-	105.5	-	91	173.3	-	105.2	-	90.9	172.1	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB550K8-525AXSP16	-	97.8	74.9	84.1	163	-	97.7	74.9	84.1	162	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB550K8-425AXSP16	58	91.4	69.6	78.5	153.8	58.3	91.3	69.7	78.4	153.2	121	20.1	1-1/2"	97	13.2	1-1/2"	145	24.7	2"
EAW-VD15S1PB750K8-625AXSP16	-	113.2	87.2	97.6	186.6	-	113.1	87.3	97.6	185.7	182	19.3	2"	145	12.7	2"	218	27.1	2"
EAW-VD15S1PB750K8-525AXSP16	-	105	80.3	90.3	175.3	67.6	104.9	80.5	90.3	174.5	145	18.2	2"	116	14.3	1-1/2"	174	25.6	2"
EAW-VD15S1PB750K8-425AXSP12	-	94.3	-	80.6	161	-	94.4	-	80.9	160.6	157	14.5	2"	126	12.2	1-1/2"	189	20.3	2"
EAW-VD15S2PB370K4-625AXSP08	-	188.5	-	-	308.5	-	187.8	-	-	306	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB370K4-525AXSP08	-	179	-	154.1	296	-	178.2	-	153.6	293.9	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB370K4-425AXSP08	-	164	125.1	140.7	275	-	163.6	125.1	140.6	273.4	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB550K4-625AXSP08	-	210.3	-	181.5	345.8	-	209.6	-	181.1	343.4	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB550K4-525AXSP08	-	199	152.5	171.2	331	-	198.7	152.6	171.2	329	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB550K4-425AXSP08	115.6	182.2	138.6	156.2	306.8	116	181.8	138.6	156.1	305	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB750K4-625AXSP08	-	225.8	173.6	194.6	371.8	-	225.6	174	194.7	370	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB750K4-525AXSP08	-	213.7	163.4	183.9	356.7	-	213.7	163.7	183.8	354.6	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB750K4-425AXSP08	123.7	195.6	148.6	167.6	329.8	124.4	195.5	148.8	167.8	328.3	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB370K5-625AXSP08	-	188.5	-	-	308.5	-	187.8	-	-	306	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB370K5-525AXSP08	-	179	-	154.1	296	-	178.2	-	153.6	293.9	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB370K5-425AXSP08	-	164	125.1	140.7	275	-	163.6	125.1	140.6	273.4	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB550K5-625AXSP08	-	210.3	-	181.5	345.8	-	209.6	-	181.1	343.4	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB550K5-525AXSP08	-	199	152.5	171.2	331	-	198.7	152.6	171.2	329	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB550K5-425AXSP08	115.6	182.2	138.6	156.2	306.8	116	181.8	138.6	156.1	305	242	15.1	3"	194	12.8	2"	291	21.2	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S2PB750K5-625AXSP08	-	225.8	173.6	194.6	371.8	-	225.6	174	194.7	370	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB750K5-525AXSP08	-	213.7	163.4	183.9	356.7	-	213.7	163.7	183.8	354.6	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB750K5-425AXSP08	123.7	195.6	148.6	167.6	329.8	124.4	195.5	148.8	167.8	328.3	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB370C4-625AXSP08	-	196.2	-	169.3	321.4	-	195.5	-	168.9	319.2	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB370C4-525AXSP08	-	186.2	142.9	160.2	308.7	-	185.7	142.7	160	306.6	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB370C4-425AXSP08	-	170.5	129.8	146.4	286.3	-	170.2	129.9	146.1	284.7	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB550C4-625AXSP08	-	221.7	170.6	191.2	365	-	221.1	170.8	190.9	363	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB550C4-525AXSP08	-	209.7	160.2	180.2	349.2	-	209	160.5	179.9	347.1	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB550C4-425AXSP08	120.9	190.8	145.1	163.6	321.9	121.3	190.3	145.3	163.5	319.9	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB750C4-625AXSP08	-	233.7	179.7	201.5	385.6	-	233.5	180.2	201.7	384.3	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB750C4-525AXSP08	141.8	221.5	169.4	190.4	370.1	142.6	221.3	169.5	190.5	368.1	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB750C4-425AXSP08	127.8	202.2	153.6	173.4	342	128.6	202.1	153.9	173.3	340.5	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB370C5-625AXSP08	-	196.2	-	169.3	321.4	-	195.5	-	168.9	319.2	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB370C5-525AXSP08	-	186.2	142.9	160.2	308.7	-	185.7	142.7	160	306.6	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB370C5-425AXSP08	-	170.5	129.8	146.4	286.3	-	170.2	129.9	146.1	284.7	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB550C5-625AXSP08	-	221.7	170.6	191.2	365	-	221.1	170.8	190.9	363	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB550C5-525AXSP08	-	209.7	160.2	180.2	349.2	-	209	160.5	179.9	347.1	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB550C5-425AXSP08	120.9	190.8	145.1	163.6	321.9	121.3	190.3	145.3	163.5	319.9	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB750C5-625AXSP08	-	233.7	179.7	201.5	385.6	-	233.5	180.2	201.7	384.3	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB750C5-525AXSP08	141.8	221.5	169.4	190.4	370.1	142.6	221.3	169.5	190.5	368.1	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB750C5-425AXSP08	127.8	202.2	153.6	173.4	342	128.6	202.1	153.9	173.3	340.5	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB370K8-625AXSP08	-	188.5	-	-	308.5	-	187.8	-	-	306	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB370K8-525AXSP08	-	179	-	154.1	296	-	178.2	-	153.6	293.9	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB370K8-425AXSP08	-	164	125.1	140.7	275	-	163.6	125.1	140.6	273.4	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB550K8-625AXSP08	-	210.3	-	181.5	345.8	-	209.6	-	181.1	343.4	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB550K8-525AXSP08	-	199	152.5	171.2	331	-	198.7	152.6	171.2	329	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB550K8-425AXSP08	115.6	182.2	138.6	156.2	306.8	116	181.8	138.6	156.1	305	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S2PB750K8-625AXSP08	-	225.8	173.6	194.6	371.8	-	225.6	174	194.7	370	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD15S2PB750K8-525AXSP08	-	213.7	163.4	183.9	356.7	-	213.7	163.7	183.8	354.6	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD15S2PB750K8-425AXSP08	123.7	195.6	148.6	167.6	329.8	124.4	195.5	148.8	167.8	328.3	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD15S3PB370K4-625AXSP06	-	284.1	-	245.6	463.2	-	282.8	-	244.8	459.5	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB370K4-525AXSP06	-	268.4	206.2	231.1	443.4	-	267.3	205.9	230.4	439.8	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB370K4-425AXSP06	156	243.8	186.1	209.4	408	156.2	242.9	186.1	208.9	405.7	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-VD15S3PB550K4-625AXSP06	-	317	244.7	273.6	519.2	-	316	244.6	273.1	515.6	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB550K4-525AXSP06	192.7	298.5	229.2	257.2	495.2	193.4	297.6	229.2	256.8	492.3	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB550K4-425AXSP04	-	264.6	-	226	450.3	-	264.6	-	226.8	448.4	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB750K4-625AXSP06	-	340	262.2	293.5	559	-	339.6	262.4	293.2	556.4	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB750K4-525AXSP06	206.3	320.6	245.9	275.8	532.9	207.3	320	245.9	275.7	530.5	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB750K4-425AXSP04	-	283.8	-	242.2	484.5	-	284.2	-	243.4	483.1	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB370K5-625AXSP06	-	284.1	-	245.6	463.2	-	282.8	-	244.8	459.5	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB370K5-525AXSP06	-	268.4	206.2	231.1	443.4	-	267.3	205.9	230.4	439.8	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB370K5-425AXSP06	156	243.8	186.1	209.4	408	156.2	242.9	186.1	208.9	405.7	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-VD15S3PB550K5-625AXSP06	-	317	244.7	273.6	519.2	-	316	244.6	273.1	515.6	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB550K5-525AXSP06	192.7	298.5	229.2	257.2	495.2	193.4	297.6	229.2	256.8	492.3	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB550K5-425AXSP04	-	264.6	-	226	450.3	-	264.6	-	226.8	448.4	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB750K5-625AXSP06	-	340	262.2	293.5	559	-	339.6	262.4	293.2	556.4	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB750K5-525AXSP06	206.3	320.6	245.9	275.8	532.9	207.3	320	245.9	275.7	530.5	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB750K5-425AXSP04	-	283.8	-	242.2	484.5	-	284.2	-	243.4	483.1	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB370C4-625AXSP06	-	295.4	228.7	255.3	483.2	-	294.4	228.2	254.7	479.3	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB370C4-525AXSP06	-	279.3	214.6	240.7	461.9	-	278.2	214.4	240	458.8	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB370C4-425AXSP06	161.7	253.3	193.4	217.4	424.6	162.1	252.5	193.2	217	421.8	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-VD15S3PB550C4-625AXSP06	-	334.3	257.7	288.3	548.8	-	332.9	257.7	287.8	545.2	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB550C4-525AXSP06	202.6	314.1	241	270.3	522.5	203	313.1	240.8	269.9	518.7	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB550C4-425AXSP04	-	276.9	-	236.5	472.9	-	277.3	-	237.3	470.9	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB750C4-625AXSP06	229.5	352.3	271.5	304	579.7	230.3	352.1	271.7	303.7	577.2	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB750C4-525AXSP06	213.4	332.2	254.5	285.6	552.9	214.6	331.9	254.7	285.8	550.7	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB750C4-425AXSP04	-	293.7	-	250.4	501.5	-	294.2	-	251.8	500.2	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB370C5-625AXSP06	-	295.4	228.7	255.3	483.2	-	294.4	228.2	254.7	479.3	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB370C5-525AXSP06	-	279.3	214.6	240.7	461.9	-	278.2	214.4	240	458.8	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB370C5-425AXSP06	161.7	253.3	193.4	217.4	424.6	162.1	252.5	193.2	217	421.8	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-VD15S3PB550C5-625AXSP06	-	334.3	257.7	288.3	548.8	-	332.9	257.7	287.8	545.2	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB550C5-525AXSP06	202.6	314.1	241	270.3	522.5	203	313.1	240.8	269.9	518.7	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB550C5-425AXSP04	-	276.9	-	236.5	472.9	-	277.3	-	237.3	470.9	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB750C5-625AXSP06	229.5	352.3	271.5	304	579.7	230.3	352.1	271.7	303.7	577.2	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB750C5-525AXSP06	213.4	332.2	254.5	285.6	552.9	214.6	331.9	254.7	285.8	550.7	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB750C5-425AXSP04	-	293.7	-	250.4	501.5	-	294.2	-	251.8	500.2	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB370K8-625AXSP06	-	284.1	-	245.6	463.2	-	282.8	-	244.8	459.5	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB370K8-525AXSP06	-	268.4	206.2	231.1	443.4	-	267.3	205.9	230.4	439.8	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB370K8-425AXSP06	156	243.8	186.1	209.4	408	156.2	242.9	186.1	208.9	405.7	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-VD15S3PB550K8-625AXSP06	-	317	244.7	273.6	519.2	-	316	244.6	273.1	515.6	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB550K8-525AXSP06	192.7	298.5	229.2	257.2	495.2	193.4	297.6	229.2	256.8	492.3	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB550K8-425AXSP04	-	264.6	-	226	450.3	-	264.6	-	226.8	448.4	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S3PB750K8-625AXSP06	-	340	262.2	293.5	559	-	339.6	262.4	293.2	556.4	484	19.2	3"	388	12.6	3"	581	23	4"
EAW-VD15S3PB750K8-525AXSP06	206.3	320.6	245.9	275.8	532.9	207.3	320	245.9	275.7	530.5	400	17.9	3"	320	11.8	3"	480	25.1	3"
EAW-VD15S3PB750K8-425AXSP04	-	283.8	-	242.2	484.5	-	284.2	-	243.4	483.1	484	14.1	3"	388	9.3	3"	581	16	4"
EAW-VD15S4PB370K4-625AXSP04	-	374.6	-	-	613.4	-	372.9	-	-	609.2	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB370K4-525AXSP04	-	355	-	305.5	588.3	-	354	-	305.1	584.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB370K4-425AXSP04	-	325.5	247.7	279.2	546.3	-	324.3	248.1	279	543.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB550K4-625AXSP04	-	417.9	-	360	687.5	-	416.6	-	359.8	682.8	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB550K4-525AXSP04	-	395.3	302.3	339.9	657.8	-	394.1	302.9	339.4	653.9	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB550K4-425AXSP04	228.7	361	274.4	309.8	608.3	230	360.8	274.9	309.6	605.7	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB750K4-625AXSP04	-	448.1	344.8	386	739.2	-	447.7	345.5	386.7	736.6	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB750K4-525AXSP04	-	424.4	324.2	364.4	707.8	-	423.7	324.8	364.9	704.5	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB750K4-425AXSP04	244.7	387.3	293.9	331.7	654.7	246.5	387.1	294.9	332.1	651.9	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB370K5-625AXSP04	-	374.6	-	-	613.4	-	372.9	-	-	609.2	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB370K5-525AXSP04	-	355	-	305.5	588.3	-	354	-	305.1	584.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB370K5-425AXSP04	-	325.5	247.7	279.2	546.3	-	324.3	248.1	279	543.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB550K5-625AXSP04	-	417.9	-	360	687.5	-	416.6	-	359.8	682.8	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB550K5-525AXSP04	-	395.3	302.3	339.9	657.8	-	394.1	302.9	339.4	653.9	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB550K5-425AXSP04	228.7	361	274.4	309.8	608.3	230	360.8	274.9	309.6	605.7	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB750K5-625AXSP04	-	448.1	344.8	386	739.2	-	447.7	345.5	386.7	736.6	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB750K5-525AXSP04	-	424.4	324.2	364.4	707.8	-	423.7	324.8	364.9	704.5	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB750K5-425AXSP04	244.7	387.3	293.9	331.7	654.7	246.5	387.1	294.9	332.1	651.9	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB370C4-625AXSP04	-	389.5	-	336.4	639.1	-	388.7	-	-	635.4	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB370C4-525AXSP04	-	369.4	283.2	318.1	613.6	-	368.5	283.4	317.8	609.4	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB370C4-425AXSP04	-	338.3	257.5	289.8	568.5	-	337.2	257.6	289.9	564.7	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB550C4-625AXSP04	-	440.1	338.8	379.3	725.7	-	439.4	338.8	379.2	721.8	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB550C4-525AXSP04	-	415.8	317.9	357.2	693	-	415.2	318.1	357.2	689.8	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB550C4-425AXSP04	239	378.5	287.6	324.4	639	240.4	377.6	287.6	324.2	635.2	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB750C4-625AXSP04	-	464.3	356.9	399.7	767.4	-	464	357.8	400.1	764.1	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB750C4-525AXSP04	280.8	439.8	335.5	377.3	734.3	282.5	439.4	336.4	378.1	731.4	606	15.1	4"	484	12.7	3"	727	21.2	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S4PB750C4-425AXSP04	252.7	401	304.4	343.1	677.9	254.7	400.9	305	343.6	675	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB370C5-625AXSP04	-	389.5	-	336.4	639.1	-	388.7	-	-	635.4	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB370C5-525AXSP04	-	369.4	283.2	318.1	613.6	-	368.5	283.4	317.8	609.4	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB370C5-425AXSP04	-	338.3	257.5	289.8	568.5	-	337.2	257.6	289.9	564.7	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB550C5-625AXSP04	-	440.1	338.8	379.3	725.7	-	439.4	338.8	379.2	721.8	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB550C5-525AXSP04	-	415.8	317.9	357.2	693	-	415.2	318.1	357.2	689.8	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB550C5-425AXSP04	239	378.5	287.6	324.4	639	240.4	377.6	287.6	324.2	635.2	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB750C5-625AXSP04	-	464.3	356.9	399.7	767.4	-	464	357.8	400.1	764.1	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB750C5-525AXSP04	280.8	439.8	335.5	377.3	734.3	282.5	439.4	336.4	378.1	731.4	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB750C5-425AXSP04	252.7	401	304.4	343.1	677.9	254.7	400.9	305	343.6	675	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB370K8-625AXSP04	-	374.6	-	-	613.4	-	372.9	-	-	609.2	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB370K8-525AXSP04	-	355	-	305.5	588.3	-	354	-	305.1	584.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB370K8-425AXSP04	-	325.5	247.7	279.2	546.3	-	324.3	248.1	279	543.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB550K8-625AXSP04	-	417.9	-	360	687.5	-	416.6	-	359.8	682.8	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB550K8-525AXSP04	-	395.3	302.3	339.9	657.8	-	394.1	302.9	339.4	653.9	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB550K8-425AXSP04	228.7	361	274.4	309.8	608.3	230	360.8	274.9	309.6	605.7	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PB750K8-625AXSP04	-	448.1	344.8	386	739.2	-	447.7	345.5	386.7	736.6	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S4PB750K8-525AXSP04	-	424.4	324.2	364.4	707.8	-	423.7	324.8	364.9	704.5	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S4PB750K8-425AXSP04	244.7	387.3	293.9	331.7	654.7	246.5	387.1	294.9	332.1	651.9	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S5PB370K4-625AXSP04	-	474	367.4	409.9	772.1	-	471.8	366.7	408.5	765.9	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB370K4-525AXSP04	292.9	449.8	346.7	387.9	740.9	293.3	447.8	345.7	386.8	735.6	606	18.1	4"	484	14.7	3"	727	25.4	4"
EAW-VD15S5PB370K4-425AXSP02	-	-	-	-	657.1	-	-	-	-	654.6	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB550K4-625AXSP04	347	529	408.9	456.7	865.4	347.7	526.6	408.2	455.7	859.4	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB550K4-525AXSP02	-	-	-	-	793.8	-	-	-	-	790.5	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB550K4-425AXSP02	-	-	-	-	730.6	-	-	-	-	729	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB750K4-625AXSP04	371.2	568.1	438.3	489.8	930.6	372.9	566.8	438.5	489.3	926.2	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB750K4-525AXSP02	-	-	-	-	853.5	-	-	-	-	851	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB750K4-425AXSP02	-	455.3	-	-	785.5	-	457.1	-	-	784.8	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB370K5-625AXSP04	-	474	367.4	409.9	772.1	-	471.8	366.7	408.5	765.9	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB370K5-525AXSP04	292.9	449.8	346.7	387.9	740.9	293.3	447.8	345.7	386.8	735.6	606	18.1	4"	484	14.7	3"	727	25.4	4"
EAW-VD15S5PB370K5-425AXSP02	-	-	-	-	657.1	-	-	-	-	654.6	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB550K5-625AXSP04	347	529	408.9	456.7	865.4	347.7	526.6	408.2	455.7	859.4	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB550K5-525AXSP02	-	-	-	-	793.8	-	-	-	-	790.5	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB550K5-425AXSP02	-	-	-	-	730.6	-	-	-	-	729	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB750K5-625AXSP04	371.2	568.1	438.3	489.8	930.6	372.9	566.8	438.5	489.3	926.2	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB750K5-525AXSP02	-	-	-	-	853.5	-	-	-	-	851	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB750K5-425AXSP02	-	455.3	-	-	785.5	-	457.1	-	-	784.8	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB370C4-625AXSP04	-	493.6	382.2	426.5	804.4	-	491.2	381.4	425	798.8	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB370C4-525AXSP04	304.3	468.1	360.3	403.4	772.8	304.8	466.2	359.5	402.3	767.5	606	18.1	4"	484	14.7	3"	727	25.4	4"
EAW-VD15S5PB370C4-425AXSP02	-	-	-	-	683.5	-	-	-	-	681.3	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB550C4-625AXSP04	365.3	557.9	430.7	481.2	913.6	365.7	555.5	430	480.4	907.5	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB550C4-525AXSP02	-	-	-	-	835.8	-	-	-	-	833.5	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB550C4-425AXSP02	-	-	-	-	766.9	-	-	-	-	765.1	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB750C4-625AXSP04	384.2	587.9	453.8	507.3	966.2	385.6	586.8	454.2	506.9	960.8	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB750C4-525AXSP02	-	-	-	-	885	-	-	-	-	883.1	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB750C4-425AXSP02	-	470.9	-	-	814	-	472.9	-	-	812.2	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB370C5-625AXSP04	-	493.6	382.2	426.5	804.4	-	491.2	381.4	425	798.8	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB370C5-525AXSP04	304.3	468.1	360.3	403.4	772.8	304.8	466.2	359.5	402.3	767.5	606	18.1	4"	484	14.7	3"	727	25.4	4"
EAW-VD15S5PB370C5-425AXSP02	-	-	-	-	683.5	-	-	-	-	681.3	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB550C5-625AXSP04	365.3	557.9	430.7	481.2	913.6	365.7	555.5	430	480.4	907.5	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB550C5-525AXSP02	-	-	-	-	835.8	-	-	-	-	833.5	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB550C5-425AXSP02	-	-	-	-	766.9	-	-	-	-	765.1	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB750C5-625AXSP04	384.2	587.9	453.8	507.3	966.2	385.6	586.8	454.2	506.9	960.8	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB750C5-525AXSP02	-	-	-	-	885	-	-	-	-	883.1	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB750C5-425AXSP02	-	470.9	-	-	814	-	472.9	-	-	812.2	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB370K8-625AXSP04	-	474	367.4	409.9	772.1	-	471.8	366.7	408.5	765.9	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB370K8-525AXSP04	292.9	449.8	346.7	387.9	740.9	293.3	447.8	345.7	386.8	735.6	606	18.1	4"	484	14.7	3"	727	25.4	4"
EAW-VD15S5PB370K8-425AXSP02	-	-	-	-	657.1	-	-	-	-	654.6	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB550K8-625AXSP04	347	529	408.9	456.7	865.4	347.7	526.6	408.2	455.7	859.4	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB550K8-525AXSP02	-	-	-	-	793.8	-	-	-	-	790.5	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB550K8-425AXSP02	-	-	-	-	730.6	-	-	-	-	729	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S5PB750K8-625AXSP04	371.2	568.1	438.3	489.8	930.6	372.9	566.8	438.5	489.3	926.2	727	19	4"	581	12.5	4"	872	26.8	4"
EAW-VD15S5PB750K8-525AXSP02	-	-	-	-	853.5	-	-	-	-	851	1211	10.1	(2) 4"	969	6.6	(2) 4"	1453	14.2	(2) 4"
EAW-VD15S5PB750K8-425AXSP02	-	455.3	-	-	785.5	-	457.1	-	-	784.8	969	9.3	(2) 4"	775	8.7	4"	1163	13.1	(2) 4"
EAW-VD15S6PB370K4-625AXSP02	-	-	-	-	900.2	-	-	-	-	895.2	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB370K4-525AXSP02	-	-	-	-	861.7	-	-	-	-	856.9	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB370K4-425AXSP02	-	468.8	-	-	796.6	-	468.8	-	-	793.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB550K4-625AXSP02	-	-	-	-	1007	-	-	-	-	1002.7	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB550K4-525AXSP02	-	570.5	-	-	961.4	-	570.8	-	-	957.3	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB550K4-425AXSP02	-	519.7	-	-	887.3	-	519.9	-	-	883.9	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB750K4-625AXSP02	-	-	-	-	1083.6	-	-	-	-	1080	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB750K4-525AXSP02	-	611.9	-	-	1033.9	-	613.1	-	-	1030.8	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB750K4-425AXSP02	-	556.9	-	475.6	952.8	-	558	-	477.4	950.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB370K5-625AXSP02	-	-	-	-	900.2	-	-	-	-	895.2	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB370K5-525AXSP02	-	-	-	-	861.7	-	-	-	-	856.9	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB370K5-425AXSP02	-	468.8	-	-	796.6	-	468.8	-	-	793.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB550K5-625AXSP02	-	-	-	-	1007	-	-	-	-	1002.7	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB550K5-525AXSP02	-	570.5	-	-	961.4	-	570.8	-	-	957.3	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB550K5-425AXSP02	-	519.7	-	-	887.3	-	519.9	-	-	883.9	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB750K5-625AXSP02	-	-	-	-	1083.6	-	-	-	-	1080	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB750K5-525AXSP02	-	611.9	-	-	1033.9	-	613.1	-	-	1030.8	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB750K5-425AXSP02	-	556.9	-	475.6	952.8	-	558	-	477.4	950.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB370C4-625AXSP02	-	-	-	-	937.7	-	-	-	-	933.5	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB370C4-525AXSP02	-	-	-	-	897.3	-	-	-	-	892.6	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB370C4-425AXSP02	-	486.8	-	-	828.7	-	487.1	-	-	824.6	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB550C4-625AXSP02	-	-	-	-	1064	-	-	-	-	1058.4	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB550C4-525AXSP02	-	599.7	-	-	1012.5	-	600	-	-	1008.1	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB550C4-425AXSP02	-	543.5	-	464.5	930.2	-	544.5	-	465.4	926.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB750C4-625AXSP02	-	-	-	-	1123.4	-	672.6	-	-	1120.1	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB750C4-525AXSP02	-	633.7	-	-	1072.3	-	634.6	-	-	1069.8	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB750C4-425AXSP02	-	576.3	-	491.6	987.6	-	577.5	-	493.6	985.3	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB370C5-625AXSP02	-	-	-	-	937.7	-	-	-	-	933.5	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB370C5-525AXSP02	-	-	-	-	897.3	-	-	-	-	892.6	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB370C5-425AXSP02	-	486.8	-	-	828.7	-	487.1	-	-	824.6	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB550C5-625AXSP02	-	-	-	-	1064	-	-	-	-	1058.4	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB550C5-525AXSP02	-	599.7	-	-	1012.5	-	600	-	-	1008.1	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB550C5-425AXSP02	-	543.5	-	464.5	930.2	-	544.5	-	465.4	926.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB750C5-625AXSP02	-	-	-	-	1123.4	-	672.6	-	-	1120.1	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB750C5-525AXSP02	-	633.7	-	-	1072.3	-	634.6	-	-	1069.8	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB750C5-425AXSP02	-	576.3	-	491.6	987.6	-	577.5	-	493.6	985.3	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB370K8-625AXSP02	-	-	-	-	900.2	-	-	-	-	895.2	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6PB370K8-525AXSP02	-	-	-	-	861.7	-	-	-	-	856.9	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB370K8-425AXSP02	-	468.8	-	-	796.6	-	468.8	-	-	793.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB550K8-625AXSP02	-	-	-	-	1007	-	-	-	-	1002.7	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB550K8-525AXSP02	-	570.5	-	-	961.4	-	570.8	-	-	957.3	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB550K8-425AXSP02	-	519.7	-	-	887.3	-	519.9	-	-	883.9	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S6PB750K8-625AXSP02	-	-	-	-	1083.6	-	-	-	-	1080	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD15S6PB750K8-525AXSP02	-	611.9	-	-	1033.9	-	613.1	-	-	1030.8	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD15S6PB750K8-425AXSP02	-	556.9	-	475.6	952.8	-	558	-	477.4	950.4	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD15S1PK370K4-625AXSP16	-	100.2	-	86.6	163.1	-	99.7	-	86.2	161.6	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK370K4-525AXSP16	-	93.3	71.8	80.4	154	-	92.8	71.6	80.1	152.8	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK370K4-425AXSP16	-	87.3	66.7	74.9	145.5	56.1	86.8	66.6	74.8	144.3	121	21.4	1-1/2"	97	14.1	1-1/2"	145	26.6	2"
EAW-VD15S1PK550K4-625AXSP16	-	112.3	86.8	96.9	183.5	-	111.8	86.7	96.6	182	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK550K4-525AXSP16	67.3	104.1	80	89.8	172.6	67.4	103.7	79.9	89.5	171.5	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK550K4-425AXSP12	-	93.7	-	80.3	158.6	-	93.5	-	80.3	157.6	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK750K4-625AXSP16	-	121.1	93.5	104.5	198.4	-	120.6	93.4	104.3	197.1	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK750K4-525AXSP12	-	109.9	-	94.2	184.1	-	109.8	-	94.4	183.4	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK750K4-425AXSP12	-	100.9	76.5	86.4	171.3	-	100.9	76.6	86.6	170.5	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK370K5-625AXSP16	-	100.2	-	86.6	163.1	-	99.7	-	86.2	161.6	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK370K5-525AXSP16	-	93.3	71.8	80.4	154	-	92.8	71.6	80.1	152.8	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK370K5-425AXSP16	-	87.3	66.7	74.9	145.5	56.1	86.8	66.6	74.8	144.3	121	21.4	1-1/2"	97	14.1	1-1/2"	145	26.6	2"
EAW-VD15S1PK550K5-625AXSP16	-	112.3	86.8	96.9	183.5	-	111.8	86.7	96.6	182	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK550K5-525AXSP16	67.3	104.1	80	89.8	172.6	67.4	103.7	79.9	89.5	171.5	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK550K5-425AXSP12	-	93.7	-	80.3	158.6	-	93.5	-	80.3	157.6	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK750K5-625AXSP16	-	121.1	93.5	104.5	198.4	-	120.6	93.4	104.3	197.1	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK750K5-525AXSP12	-	109.9	-	94.2	184.1	-	109.8	-	94.4	183.4	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK750K5-425AXSP12	-	100.9	76.5	86.4	171.3	-	100.9	76.6	86.6	170.5	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK370C4-625AXSP16	-	104.6	-	90.3	170.5	-	104	-	90.1	168.9	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK370C4-525AXSP16	-	97.1	74.7	83.7	160.6	-	96.8	74.5	83.4	159.3	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK370C4-425AXSP16	58.1	90.8	69.4	78	151.5	58.2	90.3	69.1	77.7	150.3	121	21.4	1-1/2"	97	14.1	1-1/2"	145	26.6	2"
EAW-VD15S1PK550C4-625AXSP16	-	118.6	91.5	102.4	194.1	-	118	91.4	102	192.6	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK550C4-525AXSP12	-	107.2	-	91.9	179.8	-	107	-	92	178.5	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK550C4-425AXSP12	-	98	74.3	83.9	166.2	-	97.8	74.4	83.9	165.2	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK750C4-625AXSP16	-	125.7	97	108.4	206.4	-	125.4	96.9	108.3	205.1	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK750C4-525AXSP12	-	113.9	-	97.6	191.3	-	113.9	-	97.9	190.5	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK750C4-425AXSP12	-	104.3	78.9	89.3	177.4	-	104.3	79.3	89.4	176.6	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK370C5-625AXSP16	-	104.6	-	90.3	170.5	-	104	-	90.1	168.9	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK370C5-525AXSP16	-	97.1	74.7	83.7	160.6	-	96.8	74.5	83.4	159.3	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK370C5-425AXSP16	58.1	90.8	69.4	78	151.5	58.2	90.3	69.1	77.7	150.3	121	21.4	1-1/2"	97	14.1	1-1/2"	145	26.6	2"
EAW-VD15S1PK550C5-625AXSP16	-	118.6	91.5	102.4	194.1	-	118	91.4	102	192.6	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK550C5-525AXSP12	-	107.2	-	91.9	179.8	-	107	-	92	178.5	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK550C5-425AXSP12	-	98	74.3	83.9	166.2	-	97.8	74.4	83.9	165.2	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK750C5-625AXSP16	-	125.7	97	108.4	206.4	-	125.4	96.9	108.3	205.1	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK750C5-525AXSP12	-	113.9	-	97.6	191.3	-	113.9	-	97.9	190.5	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK750C5-425AXSP12	-	104.3	78.9	89.3	177.4	-	104.3	79.3	89.4	176.6	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK370K8-625AXSP16	-	100.2	-	86.6	163.1	-	99.7	-	86.2	161.6	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK370K8-525AXSP16	-	93.3	71.8	80.4	154	-	92.8	71.6	80.1	152.8	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK370K8-425AXSP16	-	87.3	66.7	74.9	145.5	56.1	86.8	66.6	74.8	144.3	121	21.4	1-1/2"	97	14.1	1-1/2"	145	26.6	2"
EAW-VD15S1PK550K8-625AXSP16	-	112.3	86.8	96.9	183.5	-	111.8	86.7	96.6	182	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK550K8-525AXSP16	67.3	104.1	80	89.8	172.6	67.4	103.7	79.9	89.5	171.5	145	19.5	2"	116	15.2	1-1/2"	174	27.4	2"
EAW-VD15S1PK550K8-425AXSP12	-	93.7	-	80.3	158.6	-	93.5	-	80.3	157.6	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S1PK750K8-625AXSP16	-	121.1	93.5	104.5	198.4	-	120.6	93.4	104.3	197.1	182	20.6	2"	145	13.6	2"	218	29	2"
EAW-VD15S1PK750K8-525AXSP12	-	109.9	-	94.2	184.1	-	109.8	-	94.4	183.4	194	16.6	2"	155	10.9	2"	232	23.4	2"
EAW-VD15S1PK750K8-425AXSP12	-	100.9	76.5	86.4	171.3	-	100.9	76.6	86.6	170.5	157	15.5	2"	126	12.8	1-1/2"	189	21.7	2"
EAW-VD15S2PK370K4-625AXSP08	-	199.7	-	172.8	325.4	-	198.6	-	172.1	322.5	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK370K4-525AXSP08	-	189.6	145.9	163.4	312.2	-	188.5	145.5	162.7	309.7	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK370K4-425AXSP08	-	173.8	133	149.4	289.9	-	172.9	132.5	148.8	287.8	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK550K4-625AXSP08	-	223.8	173	193.4	366.2	-	222.8	172.7	192.7	363.3	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK550K4-525AXSP08	-	212	162.9	182.4	350.5	-	211.1	162.5	181.9	348.1	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK550K4-425AXSP08	123.7	193.7	147.8	166.4	324.4	124.1	192.9	147.5	165.9	322	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK750K4-625AXSP08	-	241.3	186.4	208.2	395.9	-	240.6	186.1	207.8	393.2	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK750K4-525AXSP08	147.4	228.4	175.3	196.5	378.9	147.9	227.7	175.1	196.2	376.7	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK750K4-425AXSP06	-	200.8	151.8	171.6	341	-	200.8	152.4	171.9	339.6	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S2PK370K5-625AXSP08	-	199.7	-	172.8	325.4	-	198.6	-	172.1	322.5	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK370K5-525AXSP08	-	189.6	145.9	163.4	312.2	-	188.5	145.5	162.7	309.7	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK370K5-425AXSP08	-	173.8	133	149.4	289.9	-	172.9	132.5	148.8	287.8	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK550K5-625AXSP08	-	223.8	173	193.4	366.2	-	222.8	172.7	192.7	363.3	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK550K5-525AXSP08	-	212	162.9	182.4	350.5	-	211.1	162.5	181.9	348.1	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK550K5-425AXSP08	123.7	193.7	147.8	166.4	324.4	124.1	192.9	147.5	165.9	322	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK750K5-625AXSP08	-	241.3	186.4	208.2	395.9	-	240.6	186.1	207.8	393.2	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK750K5-525AXSP08	147.4	228.4	175.3	196.5	378.9	147.9	227.7	175.1	196.2	376.7	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK750K5-425AXSP06	-	200.8	151.8	171.6	341	-	200.8	152.4	171.9	339.6	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S2PK370C4-625AXSP08	-	208.4	-	180.2	340.2	-	207.3	-	179.5	337.1	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK370C4-525AXSP08	-	197.4	152	170.3	325.9	-	196.6	151.7	169.7	323.3	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK370C4-425AXSP08	115.6	180.7	138.1	155.2	301.8	115.8	179.8	137.8	154.6	299.7	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK550C4-625AXSP08	-	236.2	182.3	203.9	386.9	-	235.2	182	203.3	384.3	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK550C4-525AXSP08	144	222.8	171.1	191.7	369.3	144.2	221.8	170.6	191.4	366.6	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK550C4-425AXSP06	-	195.1	147.7	166.9	330.9	-	194.7	148	166.9	328.9	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S2PK750C4-625AXSP08	-	250.5	193.3	216.3	411.7	-	249.8	193.4	216	409.2	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK750C4-525AXSP08	152.5	237.1	181.7	203.8	393.7	153.1	236.4	181.5	203.5	391.5	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK750C4-425AXSP06	-	207.6	157	177.6	352.7	-	207.6	157.4	177.9	351.2	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S2PK370C5-625AXSP08	-	208.4	-	180.2	340.2	-	207.3	-	179.5	337.1	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK370C5-525AXSP08	-	197.4	152	170.3	325.9	-	196.6	151.7	169.7	323.3	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK370C5-425AXSP08	115.6	180.7	138.1	155.2	301.8	115.8	179.8	137.8	154.6	299.7	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK550C5-625AXSP08	-	236.2	182.3	203.9	386.9	-	235.2	182	203.3	384.3	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK550C5-525AXSP08	144	222.8	171.1	191.7	369.3	144.2	221.8	170.6	191.4	366.6	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK550C5-425AXSP06	-	195.1	147.7	166.9	330.9	-	194.7	148	166.9	328.9	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S2PK750C5-625AXSP08	-	250.5	193.3	216.3	411.7	-	249.8	193.4	216	409.2	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK750C5-525AXSP08	152.5	237.1	181.7	203.8	393.7	153.1	236.4	181.5	203.5	391.5	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK750C5-425AXSP06	-	207.6	157	177.6	352.7	-	207.6	157.4	177.9	351.2	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S2PK370K8-625AXSP08	-	199.7	-	172.8	325.4	-	198.6	-	172.1	322.5	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK370K8-525AXSP08	-	189.6	145.9	163.4	312.2	-	188.5	145.5	162.7	309.7	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK370K8-425AXSP08	-	173.8	133	149.4	289.9	-	172.9	132.5	148.8	287.8	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK550K8-625AXSP08	-	223.8	173	193.4	366.2	-	222.8	172.7	192.7	363.3	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK550K8-525AXSP08	-	212	162.9	182.4	350.5	-	211.1	162.5	181.9	348.1	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK550K8-425AXSP08	123.7	193.7	147.8	166.4	324.4	124.1	192.9	147.5	165.9	322	242	16.5	3"	194	13.6	2"	291	23.1	3"
EAW-VD15S2PK750K8-625AXSP08	-	241.3	186.4	208.2	395.9	-	240.6	186.1	207.8	393.2	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD15S2PK750K8-525AXSP08	147.4	228.4	175.3	196.5	378.9	147.9	227.7	175.1	196.2	376.7	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD15S2PK750K8-425AXSP06	-	200.8	151.8	171.6	341	-	200.8	152.4	171.9	339.6	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD15S3PK370K4-625AXSP06	-	301	233.7	260.6	488.7	-	299	232.7	259.1	484.2	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK370K4-525AXSP06	185.5	284.3	219.2	245.1	467.2	185.6	282.8	218.6	244.1	463.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK370K4-425AXSP04	-	253.3	-	-	427.2	-	252.5	-	-	424.2	484	15.1	3"	388	9.9	3"	581	17.4	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PK550K4-625AXSP06	-	337	261.2	291.5	549.9	-	335.4	260.4	290.2	545.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK550K4-525AXSP06	206.3	317.6	244.3	273.6	524.5	206.7	316.2	243.7	272.8	520.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK550K4-425AXSP04	-	282.1	-	241.3	477.7	-	281.5	-	241.7	474.9	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK750K4-625AXSP06	238.6	363.4	281.2	314	594.6	238.7	362.2	280.7	313	590.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK750K4-525AXSP04	-	333.1	-	285.6	558.2	-	332.7	-	286.2	555.8	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK750K4-425AXSP04	-	303.7	229.8	259.7	515.3	-	303.6	230.7	260.1	513.1	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK370K5-625AXSP06	-	301	233.7	260.6	488.7	-	299	232.7	259.1	484.2	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK370K5-525AXSP06	185.5	284.3	219.2	245.1	467.2	185.6	282.8	218.6	244.1	463.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK370K5-425AXSP04	-	253.3	-	-	427.2	-	252.5	-	-	424.2	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK550K5-625AXSP06	-	337	261.2	291.5	549.9	-	335.4	260.4	290.2	545.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK550K5-525AXSP06	206.3	317.6	244.3	273.6	524.5	206.7	316.2	243.7	272.8	520.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK550K5-425AXSP04	-	282.1	-	241.3	477.7	-	281.5	-	241.7	474.9	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK750K5-625AXSP06	238.6	363.4	281.2	314	594.6	238.7	362.2	280.7	313	590.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK750K5-525AXSP04	-	333.1	-	285.6	558.2	-	332.7	-	286.2	555.8	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK750K5-425AXSP04	-	303.7	229.8	259.7	515.3	-	303.6	230.7	260.1	513.1	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK370C4-625AXSP06	-	314.1	243.6	271.7	510.8	-	312	242.6	270.2	506.3	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK370C4-525AXSP06	192.9	296.1	228.3	255.5	487.6	193	294.6	227.5	254.5	483.8	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK370C4-425AXSP04	-	263.3	-	225.3	444.7	-	262.9	-	225.4	441.6	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK550C4-625AXSP06	233.7	355.7	275.4	307.5	581.7	233.9	354.1	274.5	306.1	577	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK550C4-525AXSP04	-	324.9	-	-	544.2	-	324.5	-	-	540.9	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK550C4-425AXSP04	-	295.1	-	252.6	500	-	294.4	224	252.5	497.7	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK750C4-625AXSP06	247.3	377.6	291.5	326.2	618.3	247.7	376.2	291.2	325.3	614.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK750C4-525AXSP04	-	345.6	-	296.5	579.9	-	345.2	-	296.7	577.4	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK750C4-425AXSP04	-	314.1	237.7	268.9	533.8	-	314	238.2	269.3	531.5	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK370C5-625AXSP06	-	314.1	243.6	271.7	510.8	-	312	242.6	270.2	506.3	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK370C5-525AXSP06	192.9	296.1	228.3	255.5	487.6	193	294.6	227.5	254.5	483.8	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK370C5-425AXSP04	-	263.3	-	225.3	444.7	-	262.9	-	225.4	441.6	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK550C5-625AXSP06	233.7	355.7	275.4	307.5	581.7	233.9	354.1	274.5	306.1	577	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK550C5-525AXSP04	-	324.9	-	-	544.2	-	324.5	-	-	540.9	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK550C5-425AXSP04	-	295.1	-	252.6	500	-	294.4	224	252.5	497.7	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK750C5-625AXSP06	247.3	377.6	291.5	326.2	618.3	247.7	376.2	291.2	325.3	614.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK750C5-525AXSP04	-	345.6	-	296.5	579.9	-	345.2	-	296.7	577.4	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK750C5-425AXSP04	-	314.1	237.7	268.9	533.8	-	314	238.2	269.3	531.5	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK370K8-625AXSP06	-	301	233.7	260.6	488.7	-	299	232.7	259.1	484.2	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK370K8-525AXSP06	185.5	284.3	219.2	245.1	467.2	185.6	282.8	218.6	244.1	463.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK370K8-425AXSP04	-	253.3	-	-	427.2	-	252.5	-	-	424.2	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK550K8-625AXSP06	-	337	261.2	291.5	549.9	-	335.4	260.4	290.2	545.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK550K8-525AXSP06	206.3	317.6	244.3	273.6	524.5	206.7	316.2	243.7	272.8	520.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S3PK550K8-425AXSP04	-	282.1	-	241.3	477.7	-	281.5	-	241.7	474.9	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S3PK750K8-625AXSP06	238.6	363.4	281.2	314	594.6	238.7	362.2	280.7	313	590.5	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD15S3PK750K8-525AXSP04	-	333.1	-	285.6	558.2	-	332.7	-	286.2	555.8	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD15S3PK750K8-425AXSP04	-	303.7	229.8	259.7	515.3	-	303.6	230.7	260.1	513.1	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD15S4PK370K4-625AXSP04	-	397.1	-	343.5	647.2	-	394.8	-	342	641.3	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK370K4-525AXSP04	-	376.6	289.7	324.6	620.6	-	374.6	289	323.3	615.6	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK370K4-425AXSP04	-	344.5	263.3	296.4	575.8	-	343.2	262.9	295.3	571	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK550K4-625AXSP04	-	444.9	343.6	384.2	728.2	-	442.9	343.1	383	722.4	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK550K4-525AXSP04	-	420.6	322.9	362.2	696.7	-	418.8	322.6	361.2	691.9	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK550K4-425AXSP04	245.1	383.9	293.2	329.5	644.2	245.5	382.4	292.6	329.2	639.5	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK750K4-625AXSP04	-	479.6	369.8	413.7	787.2	-	478.1	369.7	412.9	781.8	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK750K4-525AXSP04	292.1	453	347.4	390.1	753	293.1	451.7	347.6	389.5	748.7	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK750K4-425AXSP02	-	-	-	-	660.7	-	-	-	-	659.2	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD15S4PK370K5-625AXSP04	-	397.1	-	343.5	647.2	-	394.8	-	342	641.3	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK370K5-525AXSP04	-	376.6	289.7	324.6	620.6	-	374.6	289	323.3	615.6	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK370K5-425AXSP04	-	344.5	263.3	296.4	575.8	-	343.2	262.9	295.3	571	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK550K5-625AXSP04	-	444.9	343.6	384.2	728.2	-	442.9	343.1	383	722.4	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK550K5-525AXSP04	-	420.6	322.9	362.2	696.7	-	418.8	322.6	361.2	691.9	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK550K5-425AXSP04	245.1	383.9	293.2	329.5	644.2	245.5	382.4	292.6	329.2	639.5	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK750K5-625AXSP04	-	479.6	369.8	413.7	787.2	-	478.1	369.7	412.9	781.8	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK750K5-525AXSP04	292.1	453	347.4	390.1	753	293.1	451.7	347.6	389.5	748.7	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK750K5-425AXSP02	-	-	-	-	660.7	-	-	-	-	659.2	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD15S4PK370C4-625AXSP04	-	414.3	-	358.1	676.5	-	412	-	356.7	670.5	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK370C4-525AXSP04	-	392.2	301.8	337.8	647.8	-	390.2	301.2	337	642.7	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK370C4-425AXSP04	229.2	358.1	273.8	307.9	599.5	229.7	356.9	273.4	306.8	594.5	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK550C4-625AXSP04	-	469.5	362.2	405.1	770.2	-	467.5	361.6	403.9	764.1	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK550C4-525AXSP04	285.2	442.4	339.1	380.7	734	285.8	440.5	338.7	379.5	728.6	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK550C4-425AXSP04	255.8	401.7	306.2	345	675.4	256.7	400.1	306.1	344.1	670.3	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK750C4-625AXSP04	-	497.7	383.9	429.6	818.6	-	496.5	383.5	428.6	813.5	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK750C4-525AXSP04	302.6	470.1	360.1	404.5	782.4	303.8	468.9	360.3	404	777.9	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK750C4-425AXSP02	-	-	-	-	684	-	-	-	-	682.5	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD15S4PK370C5-625AXSP04	-	414.3	-	358.1	676.5	-	412	-	356.7	670.5	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK370C5-525AXSP04	-	392.2	301.8	337.8	647.8	-	390.2	301.2	337	642.7	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK370C5-425AXSP04	229.2	358.1	273.8	307.9	599.5	229.7	356.9	273.4	306.8	594.5	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK550C5-625AXSP04	-	469.5	362.2	405.1	770.2	-	467.5	361.6	403.9	764.1	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK550C5-525AXSP04	285.2	442.4	339.1	380.7	734	285.8	440.5	338.7	379.5	728.6	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK550C5-425AXSP04	255.8	401.7	306.2	345	675.4	256.7	400.1	306.1	344.1	670.3	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK750C5-625AXSP04	-	497.7	383.9	429.6	818.6	-	496.5	383.5	428.6	813.5	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK750C5-525AXSP04	302.6	470.1	360.1	404.5	782.4	303.8	468.9	360.3	404	777.9	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK750C5-425AXSP02	-	-	-	-	684	-	-	-	-	682.5	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD15S4PK370K8-625AXSP04	-	397.1	-	343.5	647.2	-	394.8	-	342	641.3	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK370K8-525AXSP04	-	376.6	289.7	324.6	620.6	-	374.6	289	323.3	615.6	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK370K8-425AXSP04	-	344.5	263.3	296.4	575.8	-	343.2	262.9	295.3	571	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK550K8-625AXSP04	-	444.9	343.6	384.2	728.2	-	442.9	343.1	383	722.4	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK550K8-525AXSP04	-	420.6	322.9	362.2	696.7	-	418.8	322.6	361.2	691.9	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK550K8-425AXSP04	245.1	383.9	293.2	329.5	644.2	245.5	382.4	292.6	329.2	639.5	484	18.5	3"	388	12.1	3"	581	22	4"
EAW-VD15S4PK750K8-625AXSP04	-	479.6	369.8	413.7	787.2	-	478.1	369.7	412.9	781.8	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD15S4PK750K8-525AXSP04	292.1	453	347.4	390.1	753	293.1	451.7	347.6	389.5	748.7	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD15S4PK750K8-425AXSP02	-	-	-	-	660.7	-	-	-	-	659.2	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD15S5PK370K4-625AXSP04	-	502.3	390.5	434.8	814.4	-	498.8	388.3	432.3	806.2	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK370K4-525AXSP02	-	-	-	-	752.2	-	-	-	-	747.2	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK370K4-425AXSP02	-	-	-	-	694.3	-	-	-	-	690.7	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK550K4-625AXSP04	371.1	562.3	436	486.5	915.5	370.8	559.1	434.6	484.3	908.2	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK550K4-525AXSP02	-	-	-	-	842.5	-	-	-	-	839	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK550K4-425AXSP02	-	453.6	-	-	775.7	-	454.5	-	-	772.5	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK750K4-625AXSP02	-	-	-	-	955	-	-	-	-	951	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK750K4-525AXSP02	-	-	-	-	909.8	-	-	-	-	906.1	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK750K4-425AXSP02	-	488.6	-	-	837.3	-	489.7	-	-	835.2	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK370K5-625AXSP04	-	502.3	390.5	434.8	814.4	-	498.8	388.3	432.3	806.2	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK370K5-525AXSP02	-	-	-	-	752.2	-	-	-	-	747.2	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK370K5-425AXSP02	-	-	-	-	694.3	-	-	-	-	690.7	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK550K5-625AXSP04	371.1	562.3	436	486.5	915.5	370.8	559.1	434.6	484.3	908.2	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK550K5-525AXSP02	-	-	-	-	842.5	-	-	-	-	839	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S5PK550K5-425AXSP02	-	453.6	-	-	775.7	-	454.5	-	-	772.5	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK750K5-625AXSP02	-	-	-	-	955	-	-	-	-	951	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK750K5-525AXSP02	-	-	-	-	909.8	-	-	-	-	906.1	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK750K5-425AXSP02	-	488.6	-	-	837.3	-	489.7	-	-	835.2	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK370C4-625AXSP04	347.1	524.2	407.1	453.4	850.4	346.5	520.6	405.4	450.9	842.8	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK370C4-525AXSP02	-	-	-	-	783.8	-	-	-	-	779.8	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK370C4-425AXSP02	-	-	-	-	722.5	-	-	-	-	718.8	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK550C4-625AXSP02	-	-	-	-	933.5	-	-	-	-	928.5	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK550C4-525AXSP02	-	-	-	-	887.1	-	-	-	-	883.2	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK550C4-425AXSP02	-	474.2	-	-	812.7	-	475.1	-	-	809.2	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK750C4-625AXSP02	-	-	-	-	991.6	-	-	-	-	988.2	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK750C4-525AXSP02	-	-	-	-	944.9	-	-	-	-	941.1	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK750C4-425AXSP02	-	505.1	-	-	867	-	506.2	-	-	864.8	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK370C5-625AXSP04	347.1	524.2	407.1	453.4	850.4	346.5	520.6	405.4	450.9	842.8	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK370C5-525AXSP02	-	-	-	-	783.8	-	-	-	-	779.8	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK370C5-425AXSP02	-	-	-	-	722.5	-	-	-	-	718.8	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK550C5-625AXSP02	-	-	-	-	933.5	-	-	-	-	928.5	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK550C5-525AXSP02	-	-	-	-	887.1	-	-	-	-	883.2	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK550C5-425AXSP02	-	474.2	-	-	812.7	-	475.1	-	-	809.2	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK750C5-625AXSP02	-	-	-	-	991.6	-	-	-	-	988.2	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK750C5-525AXSP02	-	-	-	-	944.9	-	-	-	-	941.1	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK750C5-425AXSP02	-	505.1	-	-	867	-	506.2	-	-	864.8	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK370K8-625AXSP04	-	502.3	390.5	434.8	814.4	-	498.8	388.3	432.3	806.2	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK370K8-525AXSP02	-	-	-	-	752.2	-	-	-	-	747.2	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK370K8-425AXSP02	-	-	-	-	694.3	-	-	-	-	690.7	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK550K8-625AXSP04	371.1	562.3	436	486.5	915.5	370.8	559.1	434.6	484.3	908.2	727	20.7	4"	581	13.6	4"	872	29.1	4"
EAW-VD15S5PK550K8-525AXSP02	-	-	-	-	842.5	-	-	-	-	839	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK550K8-425AXSP02	-	453.6	-	-	775.7	-	454.5	-	-	772.5	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S5PK750K8-625AXSP02	-	-	-	-	955	-	-	-	-	951	1453	11.8	(2) 4"	1163	7.8	(2) 4"	1744	16.7	(2) 4"
EAW-VD15S5PK750K8-525AXSP02	-	-	-	-	909.8	-	-	-	-	906.1	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.4	(2) 4"
EAW-VD15S5PK750K8-425AXSP02	-	488.6	-	-	837.3	-	489.7	-	-	835.2	969	10.2	(2) 4"	775	9.3	4"	1163	14.3	(2) 4"
EAW-VD15S6PK370K4-625AXSP02	-	-	-	-	952.2	-	-	-	-	944.8	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK370K4-525AXSP02	-	-	-	-	910.6	-	-	-	-	904.5	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK370K4-425AXSP02	-	498.1	-	-	841.4	-	496.6	-	-	835.7	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK550K4-625AXSP02	-	-	-	-	1069.5	-	-	-	-	1062.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK550K4-525AXSP02	-	608.4	-	-	1020.2	-	607.9	-	-	1014.6	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK550K4-425AXSP02	-	554.2	-	473.7	940.4	-	553.3	-	474.5	935.1	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK750K4-625AXSP02	-	695.7	-	-	1155.8	-	694.7	-	-	1149.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK750K4-525AXSP02	-	655.6	-	562.5	1102	-	655	-	562.9	1095.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK750K4-425AXSP02	-	596.4	451.1	510.4	1015.4	-	596.4	452.3	511.3	1011.3	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK370K5-625AXSP02	-	-	-	-	952.2	-	-	-	-	944.8	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK370K5-525AXSP02	-	-	-	-	910.6	-	-	-	-	904.5	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK370K5-425AXSP02	-	498.1	-	-	841.4	-	496.6	-	-	835.7	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK550K5-625AXSP02	-	-	-	-	1069.5	-	-	-	-	1062.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK550K5-525AXSP02	-	608.4	-	-	1020.2	-	607.9	-	-	1014.6	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK550K5-425AXSP02	-	554.2	-	473.7	940.4	-	553.3	-	474.5	935.1	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK750K5-625AXSP02	-	695.7	-	-	1155.8	-	694.7	-	-	1149.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK750K5-525AXSP02	-	655.6	-	562.5	1102	-	655	-	562.9	1095.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK750K5-425AXSP02	-	596.4	451.1	510.4	1015.4	-	596.4	452.3	511.3	1011.3	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK370C4-625AXSP02	-	-	-	-	993.9	-	-	-	-	986.4	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK370C4-525AXSP02	-	567.9	-	-	949	-	566.8	-	-	942.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK370C4-425AXSP02	-	517.6	-	-	875.7	-	516.1	-	-	869.9	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK550C4-625AXSP02	-	681.2	-	-	1129.7	-	680.2	-	-	1123.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK550C4-525AXSP02	-	639.7	-	-	1074.3	-	639	-	-	1068.1	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK550C4-425AXSP02	-	579.6	-	495.6	985.4	-	578.5	-	496.4	979.6	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK750C4-625AXSP02	-	721.7	-	-	1200.2	-	721.2	-	-	1195.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK750C4-525AXSP02	-	680.1	-	583	1144.6	-	679.6	-	583.5	1138.4	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK750C4-425AXSP02	-	616.6	465.7	527.2	1050	-	616.7	467.7	528.2	1045.6	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK370C5-625AXSP02	-	-	-	-	993.9	-	-	-	-	986.4	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK370C5-525AXSP02	-	567.9	-	-	949	-	566.8	-	-	942.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK370C5-425AXSP02	-	517.6	-	-	875.7	-	516.1	-	-	869.9	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK550C5-625AXSP02	-	681.2	-	-	1129.7	-	680.2	-	-	1123.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK550C5-525AXSP02	-	639.7	-	-	1074.3	-	639	-	-	1068.1	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK550C5-425AXSP02	-	579.6	-	495.6	985.4	-	578.5	-	496.4	979.6	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK750C5-625AXSP02	-	721.7	-	-	1200.2	-	721.2	-	-	1195.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK750C5-525AXSP02	-	680.1	-	583	1144.6	-	679.6	-	583.5	1138.4	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK750C5-425AXSP02	-	616.6	465.7	527.2	1050	-	616.7	467.7	528.2	1045.6	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK370K8-625AXSP02	-	-	-	-	952.2	-	-	-	-	944.8	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK370K8-525AXSP02	-	-	-	-	910.6	-	-	-	-	904.5	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK370K8-425AXSP02	-	498.1	-	-	841.4	-	496.6	-	-	835.7	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK550K8-625AXSP02	-	-	-	-	1069.5	-	-	-	-	1062.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK550K8-525AXSP02	-	608.4	-	-	1020.2	-	607.9	-	-	1014.6	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK550K8-425AXSP02	-	554.2	-	473.7	940.4	-	553.3	-	474.5	935.1	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S6PK750K8-625AXSP02	-	695.7	-	-	1155.8	-	694.7	-	-	1149.5	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S6PK750K8-525AXSP02	-	655.6	-	562.5	1102	-	655	-	562.9	1095.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S6PK750K8-425AXSP02	-	596.4	451.1	510.4	1015.4	-	596.4	452.3	511.3	1011.3	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S1PI370K4-625AXSP16	-	109.8	85.5	95	177	-	108.7	85	94.4	175.1	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI370K4-525AXSP16	-	102.1	79	88.2	167.1	-	101.3	78.5	87.6	165.4	145	22.2	2"	116	16.9	1-1/2"	174	31.2	2"
EAW-VD15S1PI370K4-425AXSP12	-	92.4	-	79.4	154.3	-	91.9	-	79.1	153	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI550K4-625AXSP16	-	123.8	96.2	107.1	200.7	-	122.9	95.7	106.5	198.6	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI550K4-525AXSP12	-	112.9	-	97.1	187	-	112.3	-	96.8	185.3	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI550K4-425AXSP12	-	103.6	78.9	88.9	173.6	-	103.1	78.9	88.7	172.2	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI750K4-625AXSP12	-	132.2	-	114.2	216.8	-	131.7	-	113.7	214.9	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD15S1PI750K4-525AXSP12	-	122.4	93.7	105.3	203.4	-	121.9	93.6	105	201.8	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI750K4-425AXSP12	-	112.1	85.4	96.2	188.4	-	111.7	85.3	96	187.2	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI370K5-625AXSP16	-	109.8	85.5	95	177	-	108.7	85	94.4	175.1	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI370K5-525AXSP16	-	102.1	79	88.2	167.1	-	101.3	78.5	87.6	165.4	145	22.2	2"	116	16.9	1-1/2"	174	31.2	2"
EAW-VD15S1PI370K5-425AXSP12	-	92.4	-	79.4	154.3	-	91.9	-	79.1	153	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI550K5-625AXSP16	-	123.8	96.2	107.1	200.7	-	122.9	95.7	106.5	198.6	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI550K5-525AXSP12	-	112.9	-	97.1	187	-	112.3	-	96.8	185.3	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI550K5-425AXSP12	-	103.6	78.9	88.9	173.6	-	103.1	78.9	88.7	172.2	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI750K5-625AXSP12	-	132.2	-	114.2	216.8	-	131.7	-	113.7	214.9	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD15S1PI750K5-525AXSP12	-	122.4	93.7	105.3	203.4	-	121.9	93.6	105	201.8	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI750K5-425AXSP12	-	112.1	85.4	96.2	188.4	-	111.7	85.3	96	187.2	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI370C4-625AXSP16	-	114.7	89.3	99.4	185.3	-	113.6	88.7	98.6	183.2	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI370C4-525AXSP12	-	104.6	-	90.2	172.8	-	104	-	89.7	171.3	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI370C4-425AXSP12	-	96.2	73.4	82.6	160.8	-	95.6	73.2	82.2	159.1	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI550C4-625AXSP12	-	128.4	-	-	209.9	-	127.6	-	-	207.9	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD15S1PI550C4-525AXSP12	-	118.3	90.7	101.9	196.5	-	117.7	90.5	101.5	194.7	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI550C4-425AXSP12	-	108.2	82.4	92.8	181.6	-	107.7	82.2	92.5	180.1	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI750C4-625AXSP12	-	137.5	-	118.6	225.7	-	136.8	-	118.3	223.7	242	16.2	3"	194	13.5	2"	291	22.8	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1PI750C4-525AXSP12	-	126.9	97.2	109.1	211.1	-	126.4	97	108.9	209.4	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI750C4-425AXSP12	73.6	115.9	88.2	99.6	195.2	73.8	115.6	88.2	99.3	193.9	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI370C5-625AXSP16	-	114.7	89.3	99.4	185.3	-	113.6	88.7	98.6	183.2	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI370C5-525AXSP12	-	104.6	-	90.2	172.8	-	104	-	89.7	171.3	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI370C5-425AXSP12	-	96.2	73.4	82.6	160.8	-	95.6	73.2	82.2	159.1	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI550C5-625AXSP12	-	128.4	-	-	209.9	-	127.6	-	-	207.9	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD15S1PI550C5-525AXSP12	-	118.3	90.7	101.9	196.5	-	117.7	90.5	101.5	194.7	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI550C5-425AXSP12	-	108.2	82.4	92.8	181.6	-	107.7	82.2	92.5	180.1	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI750C5-625AXSP12	-	137.5	-	118.6	225.7	-	136.8	-	118.3	223.7	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD15S1PI750C5-525AXSP12	-	126.9	97.2	109.1	211.1	-	126.4	97	108.9	209.4	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI750C5-425AXSP12	73.6	115.9	88.2	99.6	195.2	73.8	115.6	88.2	99.3	193.9	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI370K8-625AXSP16	-	109.8	85.5	95	177	-	108.7	85	94.4	175.1	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI370K8-525AXSP12	-	102.1	79	88.2	167.1	-	101.3	78.5	87.6	165.4	145	22.2	2"	116	16.9	1-1/2"	174	31.2	2"
EAW-VD15S1PI370K8-425AXSP12	-	92.4	-	79.4	154.3	-	91.9	-	79.1	153	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI550K8-625AXSP16	-	123.8	96.2	107.1	200.7	-	122.9	95.7	106.5	198.6	182	23.3	2"	145	15.4	2"	218	32.7	2"
EAW-VD15S1PI550K8-525AXSP12	-	112.9	-	97.1	187	-	112.3	-	96.8	185.3	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI550K8-425AXSP12	-	103.6	78.9	88.9	173.6	-	103.1	78.9	88.7	172.2	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S1PI750K8-625AXSP12	-	132.2	-	114.2	216.8	-	131.7	-	113.7	214.9	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD15S1PI750K8-525AXSP12	-	122.4	93.7	105.3	203.4	-	121.9	93.6	105	201.8	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD15S1PI750K8-425AXSP12	-	112.1	85.4	96.2	188.4	-	111.7	85.3	96	187.2	157	17.5	2"	126	14.2	1-1/2"	189	24.5	2"
EAW-VD15S2PI370K4-625AXSP08	-	218.8	170.4	189.6	353.3	-	217	169.3	188.1	349.3	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI370K4-525AXSP08	-	207.4	160.5	179.2	339	-	205.8	159.7	178	335.1	303	19.7	3"	242	13	3"	363	27.7	3"
EAW-VD15S2PI370K4-425AXSP06	-	184	-	158.1	307.4	-	183.1	-	157.5	304.8	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI550K4-625AXSP08	-	247	191.9	213.7	400.4	-	245	190.9	212.3	396.4	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI550K4-525AXSP06	-	227.9	-	196.2	377.2	-	226.7	-	195.5	373.7	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI550K4-425AXSP06	-	205.9	157.1	176.9	345.2	-	205	156.7	176.2	342.6	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI750K4-625AXSP08	177	268	207.9	232	436.1	176.7	266.2	207.1	230.7	432.3	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI750K4-525AXSP06	-	247.4	189.7	212.8	410.5	-	246.4	189.2	212.2	407.1	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI750K4-425AXSP06	-	223.1	169.7	191.4	375.2	-	222.1	169.5	190.8	372.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI370K5-625AXSP08	-	218.8	170.4	189.6	353.3	-	217	169.3	188.1	349.3	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI370K5-525AXSP08	-	207.4	160.5	179.2	339	-	205.8	159.7	178	335.1	303	19.7	3"	242	13	3"	363	27.7	3"
EAW-VD15S2PI370K5-425AXSP06	-	184	-	158.1	307.4	-	183.1	-	157.5	304.8	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI550K5-625AXSP08	-	247	191.9	213.7	400.4	-	245	190.9	212.3	396.4	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI550K5-525AXSP06	-	227.9	-	196.2	377.2	-	226.7	-	195.5	373.7	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI550K5-425AXSP06	-	205.9	157.1	176.9	345.2	-	205	156.7	176.2	342.6	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI750K5-625AXSP08	177	268	207.9	232	436.1	176.7	266.2	207.1	230.7	432.3	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI750K5-525AXSP06	-	247.4	189.7	212.8	410.5	-	246.4	189.2	212.2	407.1	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI750K5-425AXSP06	-	223.1	169.7	191.4	375.2	-	222.1	169.5	190.8	372.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI370C4-625AXSP08	-	228.8	177.9	198	369.7	-	226.7	176.9	196.6	365.6	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI370C4-525AXSP08	141.9	216.4	167.3	186.9	354	141.5	214.4	166.2	185.7	349.9	303	19.7	3"	242	13	3"	363	27.7	3"
EAW-VD15S2PI370C4-425AXSP06	-	191.2	146.1	164.4	319.9	-	190.1	-	163.7	317	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI550C4-625AXSP08	172	260.2	202	225.1	422.8	171.6	258	200.8	223.7	418.2	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI550C4-525AXSP06	-	239.2	-	205.9	396.5	-	237.9	-	205	392.7	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI550C4-425AXSP06	-	215	163.8	184.6	361.2	-	214	163.6	184.1	358.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI750C4-625AXSP06	-	273.7	-	236.2	449.4	-	272.6	-	235.6	445.9	484	17.7	3"	388	11.6	3"	581	20.9	4"
EAW-VD15S2PI750C4-525AXSP06	-	256.5	196.4	220.4	426.6	-	255.6	196.3	219.9	423.1	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI750C4-425AXSP06	146.4	230.8	175.5	197.8	388.7	146.8	229.7	175.4	197.5	385.5	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI370C5-625AXSP08	-	228.8	177.9	198	369.7	-	226.7	176.9	196.6	365.6	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI370C5-525AXSP08	141.9	216.4	167.3	186.9	354	141.5	214.4	166.2	185.7	349.9	303	19.7	3"	242	13	3"	363	27.7	3"
EAW-VD15S2PI370C5-425AXSP06	-	191.2	146.1	164.4	319.9	-	190.1	-	163.7	317	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI550C5-625AXSP08	172	260.2	202	225.1	422.8	171.6	258	200.8	223.7	418.2	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI550C5-525AXSP06	-	239.2	-	205.9	396.5	-	237.9	-	205	392.7	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI550C5-425AXSP06	-	215	163.8	184.6	361.2	-	214	163.6	184.1	358.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI750C5-625AXSP06	-	273.7	-	236.2	449.4	-	272.6	-	235.6	445.9	484	17.7	3"	388	11.6	3"	581	20.9	4"
EAW-VD15S2PI750C5-525AXSP06	-	256.5	196.4	220.4	426.6	-	255.6	196.3	219.9	423.1	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI750C5-425AXSP06	146.4	230.8	175.5	197.8	388.7	146.8	229.7	175.4	197.5	385.5	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI370K8-625AXSP08	-	218.8	170.4	189.6	353.3	-	217	169.3	188.1	349.3	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI370K8-525AXSP08	-	207.4	160.5	179.2	339	-	205.8	159.7	178	335.1	303	19.7	3"	242	13	3"	363	27.7	3"
EAW-VD15S2PI370K8-425AXSP06	-	184	-	158.1	307.4	-	183.1	-	157.5	304.8	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI550K8-625AXSP08	-	247	191.9	213.7	400.4	-	245	190.9	212.3	396.4	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI550K8-525AXSP06	-	227.9	-	196.2	377.2	-	226.7	-	195.5	373.7	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI550K8-425AXSP06	-	205.9	157.1	176.9	345.2	-	205	156.7	176.2	342.6	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PI750K8-625AXSP08	177	268	207.9	232	436.1	176.7	266.2	207.1	230.7	432.3	363	20.4	3"	291	13.5	3"	436	28.7	3"
EAW-VD15S2PI750K8-525AXSP06	-	247.4	189.7	212.8	410.5	-	246.4	189.2	212.2	407.1	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD15S2PI750K8-425AXSP06	-	223.1	169.7	191.4	375.2	-	222.1	169.5	190.8	372.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S3PI370K4-625AXSP06	-	329.3	256.9	285.5	530.5	-	326.2	254.9	283.2	524	484	23.7	3"	388	15.6	3"	581	29.3	4"
EAW-VD15S3PI370K4-525AXSP04	-	304.1	-	-	501.3	-	302.1	-	-	496.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI370K4-425AXSP04	-	278.1	-	239	464.2	-	276.5	-	238	460.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI550K4-625AXSP04	-	362.5	-	-	593.2	-	360.5	-	-	587.3	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI550K4-525AXSP04	-	341.8	-	294.4	565.8	-	340	-	293.2	560.6	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI550K4-425AXSP04	-	311.6	237.6	267.5	522.1	-	310.3	237.4	266.8	518.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI750K4-625AXSP04	-	393.1	-	339.4	645.1	-	391.6	-	338.2	640.3	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI750K4-525AXSP04	-	371.2	284.5	319.2	615.8	-	369.6	283.8	318.3	611.4	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI750K4-425AXSP04	-	337.3	256.7	289.5	567.7	-	336.2	256.9	289.1	563	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI370K5-625AXSP06	-	329.3	256.9	285.5	530.5	-	326.2	254.9	283.2	524	484	23.7	3"	388	15.6	3"	581	29.3	4"
EAW-VD15S3PI370K5-525AXSP04	-	304.1	-	-	501.3	-	302.1	-	-	496.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI370K5-425AXSP04	-	278.1	-	239	464.2	-	276.5	-	238	460.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI550K5-625AXSP04	-	362.5	-	-	593.2	-	360.5	-	-	587.3	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI550K5-525AXSP04	-	341.8	-	294.4	565.8	-	340	-	293.2	560.6	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI550K5-425AXSP04	-	311.6	237.6	267.5	522.1	-	310.3	237.4	266.8	518.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI750K5-625AXSP04	-	393.1	-	339.4	645.1	-	391.6	-	338.2	640.3	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI750K5-525AXSP04	-	371.2	284.5	319.2	615.8	-	369.6	283.8	318.3	611.4	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI750K5-425AXSP04	-	337.3	256.7	289.5	567.7	-	336.2	256.9	289.1	563	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI370C4-625AXSP06	229.4	344	268.2	298.1	555.2	228.6	340.8	266.4	295.7	549	484	23.7	3"	388	15.6	3"	581	29.3	4"
EAW-VD15S3PI370C4-525AXSP04	-	317.2	-	-	523.4	-	315.2	-	-	518.1	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI370C4-425AXSP04	-	289.4	-	248.5	483.7	-	287.7	-	247.5	479.2	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI550C4-625AXSP04	-	381.8	-	-	625.5	-	379.6	-	-	619.6	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI550C4-525AXSP04	-	358.9	-	308.8	594.8	-	356.9	-	307.6	589.8	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI550C4-425AXSP04	-	325.5	247.7	279.2	546.3	-	324	247.5	278.3	541.8	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI750C4-625AXSP04	-	409	-	352.5	671.7	-	406.8	-	351.5	666.5	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI750C4-525AXSP04	-	384.8	294.6	330.7	639.9	-	383.4	294.5	329.9	634.7	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI750C4-425AXSP04	-	349	265.6	299.2	588.1	-	347.9	265.4	298.8	583.2	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI370C5-625AXSP06	229.4	344	268.2	298.1	555.2	228.6	340.8	266.4	295.7	549	484	23.7	3"	388	15.6	3"	581	29.3	4"
EAW-VD15S3PI370C5-525AXSP04	-	317.2	-	-	523.4	-	315.2	-	-	518.1	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI370C5-425AXSP04	-	289.4	-	248.5	483.7	-	287.7	-	247.5	479.2	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI550C5-625AXSP04	-	381.8	-	-	625.5	-	379.6	-	-	619.6	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI550C5-525AXSP04	-	358.9	-	308.8	594.8	-	356.9	-	307.6	589.8	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI550C5-425AXSP04	-	325.5	247.7	279.2	546.3	-	324	247.5	278.3	541.8	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI750C5-625AXSP04	-	409	-	352.5	671.7	-	406.8	-	351.5	666.5	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI750C5-525AXSP04	-	384.8	294.6	330.7	639.9	-	383.4	294.5	329.9	634.7	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI750C5-425AXSP04	-	349	265.6	299.2	588.1	-	347.9	265.4	298.8	583.2	484	17.1	3"	388	11.3	3"	581	20.2	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PI370K8-625AXSP06	-	329.3	256.9	285.5	530.5	-	326.2	254.9	283.2	524	484	23.7	3"	388	15.6	3"	581	29.3	4"
EAW-VD15S3PI370K8-525AXSP04	-	304.1	-	-	501.3	-	302.1	-	-	496.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI370K8-425AXSP04	-	278.1	-	239	464.2	-	276.5	-	238	460.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI550K8-625AXSP04	-	362.5	-	-	593.2	-	360.5	-	-	587.3	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI550K8-525AXSP04	-	341.8	-	294.4	565.8	-	340	-	293.2	560.6	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI550K8-425AXSP04	-	311.6	237.6	267.5	522.1	-	310.3	237.4	266.8	518.1	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S3PI750K8-625AXSP04	-	393.1	-	339.4	645.1	-	391.6	-	338.2	640.3	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD15S3PI750K8-525AXSP04	-	371.2	284.5	319.2	615.8	-	369.6	283.8	318.3	611.4	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD15S3PI750K8-425AXSP04	-	337.3	256.7	289.5	567.7	-	336.2	256.9	289.1	563	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD15S4PI370K4-625AXSP04	-	435	338.7	376.9	703.5	-	431.5	336.4	374.4	695.7	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI370K4-525AXSP04	-	412.2	318.7	356.1	674	-	408.5	316.7	353.7	666.3	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI370K4-425AXSP04	244.3	377.2	289.8	325	625.5	243.7	374.5	288.6	323.2	619.1	484	21.1	3"	388	13.9	3"	581	25.7	4"
EAW-VD15S4PI550K4-625AXSP04	-	491	381.4	424.8	797.3	-	487.1	379.4	421.9	789.2	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI550K4-525AXSP04	302.9	463.6	357.9	399.7	760.9	302.6	459.9	356	397.5	753.8	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI550K4-425AXSP02	-	-	-	-	673.2	-	-	-	-	669.2	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI750K4-625AXSP04	351.6	532.7	413	460.9	868.1	351.1	529.2	411.5	458.5	860.6	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI750K4-525AXSP02	-	-	-	-	796.3	-	-	-	-	790.9	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI750K4-425AXSP02	-	-	-	-	730.2	-	-	-	-	726.6	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI370K5-625AXSP04	-	435	338.7	376.9	703.5	-	431.5	336.4	374.4	695.7	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI370K5-525AXSP04	-	412.2	318.7	356.1	674	-	408.5	316.7	353.7	666.3	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI370K5-425AXSP04	244.3	377.2	289.8	325	625.5	243.7	374.5	288.6	323.2	619.1	484	21.1	3"	388	13.9	3"	581	25.7	4"
EAW-VD15S4PI550K5-625AXSP04	-	491	381.4	424.8	797.3	-	487.1	379.4	421.9	789.2	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI550K5-525AXSP04	302.9	463.6	357.9	399.7	760.9	302.6	459.9	356	397.5	753.8	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI550K5-425AXSP02	-	-	-	-	673.2	-	-	-	-	669.2	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI750K5-625AXSP04	351.6	532.7	413	460.9	868.1	351.1	529.2	411.5	458.5	860.6	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI750K5-525AXSP02	-	-	-	-	796.3	-	-	-	-	790.9	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI750K5-425AXSP02	-	-	-	-	730.2	-	-	-	-	726.6	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI370C4-625AXSP04	-	454.9	353.5	394	736.2	-	450.8	351.6	390.9	728	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI370C4-525AXSP04	281.7	429.5	332.2	371.2	703.8	281.1	426.2	330.1	368.4	696.6	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI370C4-425AXSP02	-	-	-	-	623.3	-	-	-	-	619.6	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI550C4-625AXSP04	341.3	517.3	400.9	447.3	841.7	340.6	512.9	399	444.6	832.7	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI550C4-525AXSP02	-	-	-	-	769.4	-	-	-	-	764.2	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI550C4-425AXSP02	-	-	-	-	704.1	-	-	-	-	699.5	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI750C4-625AXSP04	364.5	553.6	428.8	478.7	904	364.4	550.6	427.1	476.7	895.9	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI750C4-525AXSP02	-	-	-	-	826.1	-	-	-	-	821.9	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI750C4-425AXSP02	-	-	-	-	756.1	-	-	-	-	752.4	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI370C5-625AXSP04	-	454.9	353.5	394	736.2	-	450.8	351.6	390.9	728	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI370C5-525AXSP04	281.7	429.5	332.2	371.2	703.8	281.1	426.2	330.1	368.4	696.6	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI370C5-425AXSP02	-	-	-	-	623.3	-	-	-	-	619.6	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI550C5-625AXSP04	341.3	517.3	400.9	447.3	841.7	340.6	512.9	399	444.6	832.7	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI550C5-525AXSP02	-	-	-	-	769.4	-	-	-	-	764.2	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI550C5-425AXSP02	-	-	-	-	704.1	-	-	-	-	699.5	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI750C5-625AXSP04	364.5	553.6	428.8	478.7	904	364.4	550.6	427.1	476.7	895.9	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI750C5-525AXSP02	-	-	-	-	826.1	-	-	-	-	821.9	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI750C5-425AXSP02	-	-	-	-	756.1	-	-	-	-	752.4	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI370K8-625AXSP04	-	435	338.7	376.9	703.5	-	431.5	336.4	374.4	695.7	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI370K8-525AXSP04	-	412.2	318.7	356.1	674	-	408.5	316.7	353.7	666.3	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI370K8-425AXSP04	244.3	377.2	289.8	325	625.5	243.7	374.5	288.6	323.2	619.1	484	21.1	3"	388	13.9	3"	581	25.7	4"
EAW-VD15S4PI550K8-625AXSP04	-	491	381.4	424.8	797.3	-	487.1	379.4	421.9	789.2	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI550K8-525AXSP04	302.9	463.6	357.9	399.7	760.9	302.6	459.9	356	397.5	753.8	606	19.1	4"	484	15.4	3"	727	26.8	4"
EAW-VD15S4PI550K8-425AXSP02	-	-	-	-	673.2	-	-	-	-	669.2	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S4PI750K8-625AXSP04	351.6	532.7	413	460.9	868.1	351.1	529.2	411.5	458.5	860.6	727	20	4"	581	13.2	4"	872	28.2	4"
EAW-VD15S4PI750K8-525AXSP02	-	-	-	-	796.3	-	-	-	-	790.9	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD15S4PI750K8-425AXSP02	-	-	-	-	730.2	-	-	-	-	726.6	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD15S5PI370K4-625AXSP02	-	-	-	-	858.1	-	-	-	-	850.6	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI370K4-525AXSP02	-	-	-	-	819.7	-	-	-	-	812.5	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI370K4-425AXSP02	-	450	-	-	757.3	-	448.4	-	-	751.9	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI550K4-625AXSP02	-	-	-	-	971.9	-	-	-	-	963.4	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI550K4-525AXSP02	-	-	-	-	924.5	-	-	-	-	917.2	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI550K4-425AXSP02	-	503.6	-	-	851.1	-	502.5	-	-	844.7	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI750K4-625AXSP02	-	-	-	-	1056.6	-	-	-	-	1048.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI750K4-525AXSP02	-	600.8	-	-	1005.6	-	599.4	-	-	998.7	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI750K4-425AXSP02	-	544.6	-	466.5	923.4	-	544.1	-	466.1	918.8	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI370K5-625AXSP02	-	-	-	-	858.1	-	-	-	-	850.6	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI370K5-525AXSP02	-	-	-	-	819.7	-	-	-	-	812.5	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI370K5-425AXSP02	-	450	-	-	757.3	-	448.4	-	-	751.9	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI550K5-625AXSP02	-	-	-	-	971.9	-	-	-	-	963.4	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI550K5-525AXSP02	-	-	-	-	924.5	-	-	-	-	917.2	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI550K5-425AXSP02	-	503.6	-	-	851.1	-	502.5	-	-	844.7	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI750K5-625AXSP02	-	-	-	-	1056.6	-	-	-	-	1048.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI750K5-525AXSP02	-	600.8	-	-	1005.6	-	599.4	-	-	998.7	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI750K5-425AXSP02	-	544.6	-	466.5	923.4	-	544.1	-	466.1	918.8	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI370C4-625AXSP02	-	-	-	-	897.8	-	-	-	-	889.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI370C4-525AXSP02	-	-	-	-	855.6	-	-	-	-	848.1	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI370C4-425AXSP02	-	467.4	-	-	788.8	-	466.3	-	-	781.8	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI550C4-625AXSP02	-	-	-	-	1024.5	-	-	-	-	1016.2	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI550C4-525AXSP02	-	581.1	-	-	971.6	-	579	-	-	963.7	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI550C4-425AXSP02	-	525.9	-	450.1	890.2	-	524.5	-	449.7	883.1	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI750C4-625AXSP02	-	-	-	-	1099.9	-	-	-	-	1091.6	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI750C4-525AXSP02	-	622.7	-	-	1044.8	-	621.5	-	-	1037.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI750C4-425AXSP02	-	563.2	-	481.9	956.3	-	562.6	-	482.3	951.5	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI370C5-625AXSP02	-	-	-	-	897.8	-	-	-	-	889.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI370C5-525AXSP02	-	-	-	-	855.6	-	-	-	-	848.1	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI370C5-425AXSP02	-	467.4	-	-	788.8	-	466.3	-	-	781.8	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI550C5-625AXSP02	-	-	-	-	1024.5	-	-	-	-	1016.2	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI550C5-525AXSP02	-	581.1	-	-	971.6	-	579	-	-	963.7	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI550C5-425AXSP02	-	525.9	-	450.1	890.2	-	524.5	-	449.7	883.1	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI750C5-625AXSP02	-	-	-	-	1099.9	-	-	-	-	1091.6	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI750C5-525AXSP02	-	622.7	-	-	1044.8	-	621.5	-	-	1037.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI750C5-425AXSP02	-	563.2	-	481.9	956.3	-	562.6	-	482.3	951.5	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI370K8-625AXSP02	-	-	-	-	858.1	-	-	-	-	850.6	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI370K8-525AXSP02	-	-	-	-	819.7	-	-	-	-	812.5	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI370K8-425AXSP02	-	450	-	-	757.3	-	448.4	-	-	751.9	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI550K8-625AXSP02	-	-	-	-	971.9	-	-	-	-	963.4	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI550K8-525AXSP02	-	-	-	-	924.5	-	-	-	-	917.2	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI550K8-425AXSP02	-	503.6	-	-	851.1	-	502.5	-	-	844.7	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD15S5PI750K8-625AXSP02	-	-	-	-	1056.6	-	-	-	-	1048.9	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD15S5PI750K8-525AXSP02	-	600.8	-	-	1005.6	-	599.4	-	-	998.7	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD15S5PI750K8-425AXSP02	-	544.6	-	466.5	923.4	-	544.1	-	466.1	918.8	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD9102ZA320P7-625AXSP16	-	-	-	-	163.9	-	-	-	-	162.8	242	13.4	3"	194	11.8	2"	291	18.8	3"
EAW-VD9102ZA320P7-525AXSP16	-	89.6	-	-	151.9	-	89.6	-	-	151.1	194	15.9	2"	155	10.5	2"	232	22.4	2"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9102ZA320P7-425AXSP16	-	81.3	-	-	139.6	-	81.4	-	-	138.9	157	14.7	2"	126	12.5	1-1/2"	189	20.6	2"
EAW-VD9104ZA320P7-625AXSP12	-	203.2	156.3	175.1	334.5	-	202.3	156.1	174.7	331.9	327	17.2	3"	262	11.3	3"	392	24.1	3"
EAW-VD9104ZA320P7-525AXSP12	-	188.1	144	161.8	314.1	-	187.4	143.7	161.4	311.5	266	16.5	3"	213	14.4	2"	320	23.1	3"
EAW-VD9104ZA320P7-425AXSP12	109.1	172	130.9	147.5	290.1	109.4	171.5	130.8	147.3	288.1	218	19.7	2"	174	13	2"	262	22.5	3"
EAW-VD9106ZA320P7-625AXSP08	-	302.4	232.4	260.6	498.8	-	301.2	232.2	259.9	494.9	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD9106ZA320P7-525AXSP08	-	281.3	215.3	242	469.9	-	280.3	214.9	241.4	466	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD9106ZA320P7-425AXSP08	163	257.2	195.6	220.6	433.9	163.5	256.4	195.5	220.3	430.9	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD9108ZA320P7-625AXSP06	-	404.3	311.2	348.4	666.6	-	402.6	310.9	347.5	661.4	654	16.1	4"	523	10.6	4"	785	22.6	4"
EAW-VD9108ZA320P7-525AXSP06	-	378.9	289.8	325.5	631.4	-	377.4	289.7	324.8	627	545	15.3	4"	436	12.5	3"	654	21.5	4"
EAW-VD9108ZA320P7-425AXSP06	216.5	342.4	259.9	293.1	576.9	217.2	340.8	259.7	292.7	572.9	436	17	3"	349	11.2	3"	523	20.6	4"
EAW-VD9110ZA320P7-625AXSP04	-	496.9	-	-	824.4	-	495.6	-	-	818.9	981	12.4	(2) 4"	785	10.9	4"	1177	17.5	(2) 4"
EAW-VD9110ZA320P7-525AXSP04	-	462.9	-	397.1	777	-	461.9	-	397	771.7	812	14.9	4"	649	9.8	4"	974	16.8	(2) 4"
EAW-VD9110ZA320P7-425AXSP04	-	418.9	317.2	358.7	711.5	-	418.5	317.7	358.4	707.9	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD9112ZA320P7-625AXSP04	-	604.1	464.2	520.4	996.4	-	601.6	463.8	519.1	988.6	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD9112ZA320P7-525AXSP04	-	563.5	430.6	483.9	939.7	-	560.6	429.8	482.9	933.2	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD9112ZA320P7-425AXSP04	322.9	510.2	387.7	437.3	861.5	324	508.8	387.5	436.8	855.7	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD9114ZA320P7-625AXSP04	463.8	711.1	548.5	613.8	1168	464.6	707.3	547.1	611.3	1158.8	981	16.4	(2) 4"	785	13.6	4"	1177	23.1	(2) 4"
EAW-VD9114ZA320P7-525AXSP04	427.5	663.1	508.7	570.6	1102.1	428	660.5	507.7	569.2	1093	812	18.9	4"	649	12.4	4"	974	22.4	(2) 4"
EAW-VD9114ZA320P7-425AXSP02	-	-	-	-	960.6	-	-	-	-	957.6	1308	10	(2) 4"	1046	6.6	(2) 4"	1570	14.1	(2) 4"
EAW-VD9116ZA320P7-625AXSP02	-	-	-	-	1288.9	-	-	-	-	1282.2	1962	11	(3) 4"	1570	9.3	(2) 4"	2354	15.5	(3) 4"
EAW-VD9116ZA320P7-525AXSP02	-	-	-	-	1216.9	-	-	-	-	1210.5	1635	12.4	(2) 4"	1308	8.2	(2) 4"	1962	14.4	(3) 4"
EAW-VD9116ZA320P7-425AXSP02	-	643.5	-	-	1108	-	644.5	-	-	1102.7	1308	11	(2) 4"	1046	7.2	(2) 4"	1570	15.5	(2) 4"
EAW-VD9118ZA320P7-625AXSP02	-	-	-	-	1458.9	-	-	-	-	1449.5	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD9118ZA320P7-525AXSP02	-	815	-	-	1378.2	-	814.8	-	-	1369.1	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD9118ZA320P7-425AXSP02	-	734	-	626.2	1254.1	-	733.7	-	627.2	1248	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD9120ZA320P7-625AXSP02	-	979.4	-	-	1629	-	977.1	-	-	1618.4	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD9120ZA320P7-525AXSP02	-	913.6	-	783.2	1537.5	-	913.2	-	784.3	1529.2	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD9120ZA320P7-425AXSP02	-	822.5	621.5	703.4	1401.9	-	822	622.8	704.3	1392.9	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD9102ZJ320P7-625AXSP16	-	-	-	-	172.5	-	-	-	-	171.2	242	14.3	3"	194	12.3	2"	291	20	3"
EAW-VD9102ZJ320P7-525AXSP16	-	95.1	-	-	160.2	-	94.9	-	-	158.9	194	16.8	2"	155	11.1	2"	232	23.6	2"
EAW-VD9102ZJ320P7-425AXSP16	-	86.3	-	73.7	146.9	-	86.1	-	73.8	146	157	15.6	2"	126	13.1	1-1/2"	189	21.9	2"
EAW-VD9104ZJ320P7-625AXSP12	-	214.7	165.7	185.3	351.7	-	213.2	165.3	184.5	348.4	327	18.5	3"	262	12.2	3"	392	26	3"
EAW-VD9104ZJ320P7-525AXSP12	128.5	199	152.5	171.2	330.1	128.4	197.7	152.2	170.5	327	266	17.8	3"	213	15.3	2"	320	25	3"
EAW-VD9104ZJ320P7-425AXSP08	-	175.8	-	-	299.1	-	175.4	-	-	296.8	327	13	3"	262	8.5	3"	392	18.2	3"
EAW-VD9106ZJ320P7-625AXSP08	-	319.6	246.5	275.8	524.4	-	317.5	245.9	274.6	519.6	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD9106ZJ320P7-525AXSP08	192.1	297.6	228.4	256	493.9	192	295.7	227.6	255.1	489.2	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD9106ZJ320P7-425AXSP06	-	265.4	-	227.3	450	-	264.7	-	227.2	446.4	436	15	3"	349	9.9	3"	523	17.8	4"
EAW-VD9108ZJ320P7-625AXSP06	-	427.8	330.1	369.2	700.8	-	424.9	328.8	367.1	694.3	654	17.4	4"	523	11.5	4"	785	24.5	4"
EAW-VD9108ZJ320P7-525AXSP06	258.5	400.2	307.3	344.4	663.6	258.4	398	306.2	343	658.1	545	16.6	4"	436	13.3	3"	654	23.4	4"
EAW-VD9108ZJ320P7-425AXSP06	230.3	361.2	275.6	310.3	606.9	230.6	359.7	275	309	602	436	18.4	3"	349	12.1	3"	523	22.5	4"
EAW-VD9110ZJ320P7-625AXSP04	-	526	-	-	867.9	-	523.2	-	-	859.9	981	13.5	(2) 4"	785	11.7	4"	1177	19	(2) 4"
EAW-VD9110ZJ320P7-525AXSP04	-	489.8	-	421	818	-	488	-	420.1	811.2	812	16	4"	649	10.5	4"	974	18.4	(2) 4"
EAW-VD9110ZJ320P7-425AXSP04	-	443.7	336.6	380.1	748.8	-	441.9	336.6	379.2	744	654	14.7	4"	523	9.7	4"	785	20.6	4"
EAW-VD9112ZJ320P7-625AXSP04	-	638.5	492.4	550.8	1047.6	-	634.1	491.1	548.5	1037.9	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD9112ZJ320P7-525AXSP04	383.5	595.3	456.1	512	987.9	384	592.1	455.2	510.1	979.7	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD9112ZJ320P7-425AXSP04	343.6	539.3	411.2	462.4	905.1	344.1	536.2	410.3	461.2	897.9	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD9114ZJ320P7-625AXSP04	493.5	751.5	580.8	648.6	1227.9	492.8	745.4	578.5	645	1215.1	981	18	(2) 4"	785	14.6	4"	1177	25.2	(2) 4"
EAW-VD9114ZJ320P7-525AXSP02	-	-	-	-	1114.2	-	-	-	-	1106.8	1635	12.2	(2) 4"	1308	8	(2) 4"	1962	14.1	(3) 4"
EAW-VD9114ZJ320P7-425AXSP02	-	-	-	-	1013.5	-	-	-	-	1007.4	1308	10.8	(2) 4"	1046	7.1	(2) 4"	1570	15.2	(2) 4"
EAW-VD9116ZJ320P7-625AXSP02	-	-	-	-	1359.1	-	-	-	-	1348.5	1962	11.9	(3) 4"	1570	9.8	(2) 4"	2354	16.7	(3) 4"
EAW-VD9116ZJ320P7-525AXSP02	-	760.5	-	-	1281.8	-	759.1	-	-	1273.2	1635	13.3	(2) 4"	1308	8.7	(2) 4"	1962	15.6	(3) 4"
EAW-VD9116ZJ320P7-425AXSP02	-	683.7	-	-	1166.9	-	682.5	-	-	1159.8	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD9118ZJ320P7-625AXSP02	-	926.2	-	-	1538.2	-	922.7	-	-	1524.3	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD9118ZJ320P7-525AXSP02	-	864.3	-	-	1451.5	-	861.3	-	-	1439.8	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD9118ZJ320P7-425AXSP02	-	778.1	-	665.5	1320.6	-	775.3	-	664.3	1312.5	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD9102PA320P7-625AXSP16	-	-	-	-	140.6	-	-	-	-	140.2	182	15.3	2"	145	10.1	2"	218	21.5	2"
EAW-VD9102PA320P7-525AXSP16	-	76.8	-	-	130.9	-	77	-	-	130.6	145	14.2	2"	116	11.6	1-1/2"	174	20	2"
EAW-VD9102PA320P7-425AXSP16	-	71.2	-	60.7	122.5	-	71.4	-	61	122.2	121	16.1	1-1/2"	97	10.6	1-1/2"	145	19.1	2"
EAW-VD9104PA320P7-625AXSP12	-	172.6	132.6	148.6	286.2	112.1	172.6	132.8	148.8	284.6	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD9104PA320P7-525AXSP12	101.2	158.8	121.1	136.2	266.6	101.6	158.6	121.2	136.3	265.5	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD9104PA320P7-425AXSP08	-	141.7	-	120.7	243.9	-	142.2	-	121.4	243.6	242	11.1	3"	194	10.1	2"	291	15.6	3"
EAW-VD9106PA320P7-625AXSP08	-	258.6	198.3	222.6	428.3	-	258.2	198.6	222.6	426.4	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD9106PA320P7-525AXSP08	154.9	242.9	185.3	208.6	407.2	155.8	242.9	185.8	208.7	405.3	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD9106PA320P7-425AXSP06	-	211	158.7	179.9	361.8	-	211.4	159.5	180.7	360.9	315	12.3	3"	252	8.1	3"	378	17.3	3"
EAW-VD9108PA320P7-625AXSP06	-	343.8	263.6	296	569.6	-	343.3	264	295.9	567.2	484	17.7	3"	388	11.6	3"	581	20.9	4"
EAW-VD9108PA320P7-525AXSP06	204.8	321.4	245.1	276	539.2	206	321	245.7	276.1	536.8	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD9108PA320P7-425AXSP04	-	280.3	-	239	483.9	-	281.4	-	240.4	482.7	484	13.1	3"	388	8.6	3"	581	14.6	4"
EAW-VD9110PA320P7-625AXSP04	-	421.7	-	362.6	704.1	-	422.3	-	363.1	701.2	727	14.1	4"	581	9.2	4"	872	19.8	4"
EAW-VD9110PA320P7-525AXSP04	-	396.3	300.7	339.4	668.5	-	396.5	302.1	340.2	666.4	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD9110PA320P7-425AXSP04	-	358.7	270.5	306.3	612.6	225.4	358.7	271.7	306.8	610	484	15.1	3"	388	9.9	3"	581	17.4	4"
EAW-VD9112PA320P7-625AXSP04	-	513	393.6	441.4	851.3	-	512.2	394.3	442	847.7	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD9112PA320P7-525AXSP04	306.7	482.1	367.6	414	808.8	308.5	481.6	368.5	414.1	805.2	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD9112PA320P7-425AXSP02	-	-	-	-	699.1	-	-	-	-	698.8	969	7.8	(2) 4"	775	7.8	4"	1163	11	(2) 4"
EAW-VD9114PA320P7-625AXSP04	391.9	604.1	464.7	520.9	998.1	393.6	603.2	464.7	520.8	993.8	727	18	4"	581	11.9	4"	872	25.4	4"
EAW-VD9114PA320P7-525AXSP02	-	-	-	-	903.6	-	-	-	-	902.5	1211	9.6	(2) 4"	969	6.3	(2) 4"	1453	13.5	(2) 4"
EAW-VD9114PA320P7-425AXSP02	-	473.6	-	-	825.1	-	476.7	-	-	823.3	969	8.8	(2) 4"	775	8.4	4"	1163	12.4	(2) 4"
EAW-VD9116PA320P7-625AXSP02	-	-	-	-	1099.8	-	-	-	-	1096.9	1453	11.5	(2) 4"	1163	7.6	(2) 4"	1744	16.2	(2) 4"
EAW-VD9116PA320P7-525AXSP02	-	609.8	-	-	1041.5	-	611.5	-	-	1038.7	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD9116PA320P7-425AXSP02	-	550.4	-	467.7	950.7	-	551.8	-	470.8	948.6	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD9118PA320P7-625AXSP02	-	740.3	-	-	1245.2	-	742.7	-	-	1241.8	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD9118PA320P7-525AXSP02	-	693.7	-	593.1	1180	-	695.5	-	595.7	1176.7	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD9118PA320P7-425AXSP02	-	626.1	470.3	534.6	1076.6	-	628.7	473.6	536.9	1074	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD9120PA320P7-625AXSP02	-	830.6	-	713.5	1390.6	-	832.1	-	714.8	1385	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD9120PA320P7-525AXSP02	-	778	590.2	666.7	1316.6	-	779.9	593.1	668.4	1312.9	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD9120PA320P7-425AXSP02	-	703.3	529.5	600.9	1203.9	-	704.8	532.9	602.3	1199.1	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD9102PJ320P7-625AXSP16	-	89.8	-	-	150.1	-	89.8	-	-	149.4	182	16.2	2"	145	10.7	2"	218	22.8	2"
EAW-VD9102PJ320P7-525AXSP16	-	82.5	-	70.5	139.5	-	82.4	-	70.7	138.9	145	15.1	2"	116	12.2	1-1/2"	174	21.2	2"
EAW-VD9102PJ320P7-425AXSP16	-	76.3	57.4	65.1	130.3	-	76.3	57.8	65.3	130	121	17	1-1/2"	97	11.2	1-1/2"	145	20.4	2"
EAW-VD9104PJ320P7-625AXSP12	120.1	184.9	142.3	159.2	304.5	120.4	184.1	142.1	158.9	302.8	242	17.6	3"	194	14.4	2"	291	24.6	3"
EAW-VD9104PJ320P7-525AXSP08	-	168	-	143.8	284	-	168.1	-	144.1	282.8	303	12.6	3"	242	8.3	3"	363	17.7	3"
EAW-VD9104PJ320P7-425AXSP08	-	151.8	114.3	129.6	259.9	-	152.1	114.9	130.1	258.8	242	12	3"	194	10.7	2"	291	16.9	3"
EAW-VD9106PJ320P7-625AXSP08	179.6	276.6	212.8	238.4	456.2	180.1	275.8	212.8	238	453.1	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD9106PJ320P7-525AXSP06	-	252.3	191.9	216.4	424.9	-	252.1	192.4	216.5	423	400	14.4	3"	320	9.5	3"	480	20.2	3"
EAW-VD9106PJ320P7-425AXSP06	-	225.7	170.5	192.9	385	-	225.8	171	193.3	383.4	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD9108PJ320P7-625AXSP06	238.7	367.8	283	317	606.8	239.4	366.7	283	316.5	602.7	484	19	3"	388	12.5	3"	581	22.8	4"
EAW-VD9108PJ320P7-525AXSP04	-	332.9	-	284.8	563.4	-	333.2	-	285.5	561	606	12	4"	484	10.7	3"	727	16.9	4"
EAW-VD9108PJ320P7-425AXSP04	-	300.9	226.4	256.7	515	-	301	227.5	257.3	513.6	484	14	3"	388	9.2	3"	581	15.8	4"
EAW-VD9110PJ320P7-625AXSP04	-	451.9	346.6	389.1	750.3	-	451.2	346.7	389.1	746.1	727	15.2	4"	581	10	4"	872	21.3	4"
EAW-VD9110PJ320P7-525AXSP04	-	423.7	323	364.1	712	-	423.3	323.8	363.7	707.9	606	14.2	4"	484	12.2	3"	727	20	4"
EAW-VD9110PJ320P7-425AXSP04	240.6	383.4	290.3	328.1	650.7	242.3	382.8	291	328.1	647.9	484	16.2	3"	388	10.7	3"	581	18.9	4"
EAW-VD9112PJ320P7-625AXSP04	356	548.8	422	472.8	907	357	547.2	422.1	472.1	900.8	727	17.4	4"	581	11.4	4"	872	24.4	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9112PJ320P7-525AXSP02	-	-	-	-	818.6	-	-	-	-	816.5	1211	9.3	(2) 4"	969	6.1	(2) 4"	1453	13	(2) 4"
EAW-VD9112PJ320P7-425AXSP02	-	-	-	-	745.9	-	-	-	-	744.4	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD9114PJ320P7-625AXSP02	-	-	-	-	1020.7	-	-	-	-	1016.6	1453	11.3	(2) 4"	1163	7.4	(2) 4"	1744	15.9	(2) 4"
EAW-VD9114PJ320P7-525AXSP02	-	564.9	-	-	964.5	-	566.5	-	-	961.9	1211	10.4	(2) 4"	969	6.8	(2) 4"	1453	14.6	(2) 4"
EAW-VD9114PJ320P7-425AXSP02	-	509.1	-	-	878.7	-	510.5	-	-	876.7	969	9.6	(2) 4"	775	8.9	4"	1163	13.5	(2) 4"
EAW-VD9116PJ320P7-625AXSP02	-	699.8	-	-	1173.9	-	700	-	-	1169	1453	12.4	(2) 4"	1163	8.1	(2) 4"	1744	17.5	(2) 4"
EAW-VD9116PJ320P7-525AXSP02	-	654.7	-	-	1109.9	-	655.4	-	561.1	1106.8	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD9116PJ320P7-425AXSP02	-	590.2	-	502.8	1012.2	-	590.6	-	505.1	1009.8	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD9118PJ320P7-625AXSP02	-	794.9	-	682.4	1328.9	-	795.1	-	683.7	1321.7	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD9118PJ320P7-525AXSP02	-	744.5	564.1	637.7	1257.3	-	744	566.9	638.4	1252	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD9118PJ320P7-425AXSP02	-	671.2	506.4	573.3	1146	-	671.5	508	574.6	1141.4	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD91S1MA320P7-625AXSP16	-	-	-	-	80.5	-	-	-	-	80	109	15.9	1-1/2"	87	10.5	1-1/2"	131	22.4	1-1/2"
EAW-VD91S1MA320P7-525AXSP16	-	44.9	-	-	76	-	44.9	-	-	75.6	97	14.6	1-1/2"	78	9.6	1-1/2"	116	20.5	1-1/2"
EAW-VD91S1MA320P7-425AXSP16	-	40.6	-	34.7	69.5	-	40.7	-	34.8	69.1	73	14.3	1-1/2"	58	9.5	1-1/2"	87	20.1	1-1/2"
EAW-VD91S2MA320P7-625AXSP12	-	99.7	76.7	86	164.4	-	99.3	76.7	85.7	163.1	157	17.3	2"	126	13.9	1-1/2"	189	24.3	2"
EAW-VD91S2MA320P7-525AXSP12	60.5	94	72	80.9	156.3	60.6	93.6	71.9	80.7	155.1	121	20	1-1/2"	97	13.2	1-1/2"	145	24.9	2"
EAW-VD91S2MA320P7-425AXSP08	-	81.4	-	-	139.6	-	81.3	-	-	138.7	157	12.2	2"	126	10.5	1-1/2"	189	17.2	2"
EAW-VD91S3MA320P7-625AXSP08	-	147.4	113.3	127.1	243.6	-	146.8	113.2	126.8	241.8	230	18.6	2"	184	12.3	2"	276	21	3"
EAW-VD91S3MA320P7-525AXSP08	-	138.7	106	119.3	231.4	-	138.3	106	118.9	229.9	194	17.3	2"	155	11.4	2"	232	24.4	2"
EAW-VD91S3MA320P7-425AXSP08	80	126.4	96	108.3	213.4	80.3	126.1	96	108.2	211.7	157	16.2	2"	126	13.2	1-1/2"	189	22.8	2"
EAW-VD91S4MA320P7-625AXSP06	-	198.5	152.6	171	327.5	-	197.8	152.5	170.7	325.1	315	15.2	3"	252	10.1	3"	378	21.4	3"
EAW-VD91S4MA320P7-525AXSP06	-	182.9	139.7	157.1	305.8	-	182.3	139.8	156.9	303.4	254	14.6	3"	204	12.5	2"	305	20.6	3"
EAW-VD91S4MA320P7-425AXSP06	105	166.1	126.2	142.4	280.8	105.3	165.7	126.2	142.1	278.6	206	17.2	2"	165	11.3	2"	247	20	3"
EAW-VD91S5MA320P7-625AXSP04	-	243.7	-	-	405	-	243.2	-	-	402	472	14.8	3"	378	9.7	3"	567	17.2	4"
EAW-VD91S5MA320P7-525AXSP04	-	226.2	-	194	380.7	-	225.9	-	194	378.2	388	13.6	3"	310	8.9	3"	465	19.1	3"
EAW-VD91S5MA320P7-425AXSP04	-	205.8	155.7	176.2	349.9	-	205.4	156	176.1	347.8	315	12.7	3"	252	8.4	3"	378	17.8	3"
EAW-VD91S6MA320P7-625AXSP04	-	296.3	227.9	255.2	489.5	-	295.2	227.8	254.6	485.9	472	16.8	3"	378	11	3"	567	20	4"
EAW-VD91S6MA320P7-525AXSP04	-	275.5	210.2	236.4	459.9	-	274.2	210.3	236	456.9	388	15.6	3"	310	10.2	3"	465	21.9	3"
EAW-VD91S6MA320P7-425AXSP04	158.5	250.7	190.3	214.8	423.1	159.1	249.7	190.3	214.3	420.4	315	14.7	3"	252	9.7	3"	378	20.6	3"
EAW-VD9102ZA247I6-625AXSP16	-	-	-	-	144	-	-	-	-	143.1	242	13.4	3"	194	11.8	2"	291	18.8	3"
EAW-VD9102ZA247I6-525AXSP16	-	-	-	-	134.9	-	-	-	-	134.2	194	15.9	2"	155	10.5	2"	232	22.4	2"
EAW-VD9102ZA247I6-425AXSP16	-	73.2	-	-	125	-	73.2	-	-	124.2	157	14.7	2"	126	12.5	1-1/2"	189	20.6	2"
EAW-VD9104ZA247I6-625AXSP12	-	179.3	-	154.9	294.1	-	178.6	-	154.3	291.6	327	17.2	3"	262	11.3	3"	392	24.1	3"
EAW-VD9104ZA247I6-525AXSP12	-	167.6	128.4	144.1	278.1	-	166.8	128.2	143.8	275.9	266	16.5	3"	213	14.4	2"	320	23.1	3"
EAW-VD9104ZA247I6-425AXSP12	-	154.5	117.7	132.7	259.4	-	154.1	117.6	132.3	257.8	218	19.7	2"	174	13	2"	262	22.5	3"
EAW-VD9106ZA247I6-625AXSP08	-	266.9	-	230.5	438	-	266	-	229.7	434.9	484	18.4	3"	388	12.1	3"	581	21.7	4"
EAW-VD9106ZA247I6-525AXSP08	-	250.7	192.1	215.5	416.2	-	249.8	192	215.1	413.4	400	17	3"	320	11.2	3"	480	23.9	3"
EAW-VD9106ZA247I6-425AXSP08	-	231	175.9	198.4	388.1	-	230.4	175.8	197.8	385.6	327	16.1	3"	262	10.6	3"	392	22.6	3"
EAW-VD9108ZA247I6-625AXSP08	238.7	361.7	280.4	312.6	588.8	238.5	359.5	279.5	311.4	583.9	484	22.4	3"	388	14.7	3"	581	27.3	4"
EAW-VD9108ZA247I6-525AXSP06	-	337.1	258.4	289.9	559.8	-	335.8	258.3	289.2	555.3	545	15.3	4"	436	12.5	3"	654	21.5	4"
EAW-VD9108ZA247I6-425AXSP06	-	307.1	233.8	263.6	516.7	-	306.2	234.1	263.3	512.7	436	17	3"	349	11.2	3"	523	20.6	4"
EAW-VD9110ZA247I6-625AXSP06	-	452.1	350.1	390.7	736.8	-	449.3	349.3	389.3	730.7	654	19.1	4"	523	12.6	4"	785	26.8	4"
EAW-VD9110ZA247I6-525AXSP04	-	412.1	-	-	689.2	-	411.3	-	-	684.7	812	14.9	4"	649	9.8	4"	974	16.8	(2) 4"
EAW-VD9110ZA247I6-425AXSP04	-	376.7	-	322.4	637.7	-	375.8	-	322.7	633.7	654	13.5	4"	523	8.9	4"	785	19.1	4"
EAW-VD9112ZA247I6-625AXSP04	-	533.2	-	460.3	875.1	-	531.3	-	458.8	868.8	981	14.4	(2) 4"	785	12.3	4"	1177	20.3	(2) 4"
EAW-VD9112ZA247I6-525AXSP04	-	501.5	384.2	431.1	833.4	-	499.6	384.1	430.2	826.8	812	16.9	4"	649	11.1	4"	974	19.6	(2) 4"
EAW-VD9112ZA247I6-425AXSP04	-	458.5	348.9	392.8	770.7	-	456.5	348.7	392.4	765.8	654	15.5	4"	523	10.2	4"	785	21.9	4"
EAW-VD9114ZA247I6-625AXSP04	-	628.3	485.5	542.7	1026.8	-	624.5	484.6	540.8	1018.3	981	16.4	(2) 4"	785	13.6	4"	1177	23.1	(2) 4"
EAW-VD9114ZA247I6-525AXSP04	382.4	590.7	453.6	508.8	977.1	382.7	587.7	452.7	506.9	969.4	812	18.9	4"	649	12.4	4"	974	22.4	(2) 4"
EAW-VD9114ZA247I6-425AXSP04	345.2	539.9	412.7	463.6	904.2	346.1	537.6	411.7	462.3	897.1	654	17.5	4"	523	11.6	4"	785	24.6	4"
EAW-VD9116ZA247I6-625AXSP04	476.2	722.5	560.1	625.1	1177.6	476.3	718	558.2	622	1167.7	981	18.4	(2) 4"	785	14.9	4"	1177	25.8	(2) 4"
EAW-VD9116ZA247I6-525AXSP02	-	-	-	-	1080.3	-	-	-	-	1073.5	1635	12.4	(2) 4"	1308	8.2	(2) 4"	1962	14.4	(3) 4"
EAW-VD9116ZA247I6-425AXSP02	-	-	-	-	992.6	-	-	-	-	988.2	1308	11	(2) 4"	1046	7.2	(2) 4"	1570	15.5	(2) 4"
EAW-VD9118ZA247I6-625AXSP02	-	-	-	-	1283.7	-	-	-	-	1276.3	1962	12	(3) 4"	1570	9.9	(2) 4"	2354	16.9	(3) 4"
EAW-VD9118ZA247I6-525AXSP02	-	-	-	-	1221.7	-	-	-	-	1215.4	1635	13.4	(2) 4"	1308	8.8	(2) 4"	1962	15.8	(3) 4"
EAW-VD9118ZA247I6-425AXSP02	-	659.8	-	-	1123.3	-	659.5	-	-	1118.2	1308	12	(2) 4"	1046	7.9	(2) 4"	1570	16.9	(2) 4"
EAW-VD9120ZA247I6-625AXSP02	-	-	-	-	1433.1	-	-	-	-	1423.1	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD9120ZA247I6-525AXSP02	-	815.1	-	-	1364.4	-	813.5	-	-	1355.6	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD9120ZA247I6-425AXSP02	-	740.2	-	632.8	1255.3	-	738.6	-	633.7	1247.7	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD9102ZJ247I6-625AXSP16	-	-	-	-	152	-	-	-	-	150.6	242	14.3	3"	194	12.3	2"	291	20	3"
EAW-VD9102ZJ247I6-525AXSP16	-	-	-	-	142.2	-	-	-	-	141.3	194	16.8	2"	155	11.1	2"	232	23.6	2"
EAW-VD9102ZJ247I6-425AXSP16	-	77.6	-	-	131.7	-	77.6	-	-	130.9	157	15.6	2"	126	13.1	1-1/2"	189	21.9	2"
EAW-VD9104ZJ247I6-625AXSP12	-	189.6	-	164	309.2	-	188.4	-	163.1	306.4	327	18.5	3"	262	12.2	3"	392	26	3"
EAW-VD9104ZJ247I6-525AXSP12	-	177.2	136.3	152.6	292.7	-	176.1	135.9	152	290.1	266	17.8	3"	213	15.3	2"	320	25	3"
EAW-VD9104ZJ247I6-425AXSP12	104.7	163.3	124.8	140.3	273.2	104.8	162.6	124.5	139.9	270.6	218	21.1	2"	174	13.9	2"	262	24.4	3"
EAW-VD9106ZJ247I6-625AXSP08	-	282.4	-	244.1	461.2	-	280.9	-	242.8	456.6	484	19.7	3"	388	13	3"	581	23.6	4"
EAW-VD9106ZJ247I6-525AXSP08	-	265.1	203.8	228.5	438	-	263.8	203.2	227.4	434	400	18.4	3"	320	12.1	3"	480	25.8	3"
EAW-VD9106ZJ247I6-425AXSP08	156.5	244.3	186.9	210.1	408.6	156.6	243.2	186.1	209.1	404.8	327	17.4	3"	262	11.5	3"	392	24.4	3"
EAW-VD9108ZJ247I6-625AXSP06	-	377.9	-	326.3	616.3	-	375.4	-	325	610.8	654	17.4	4"	523	11.5	4"	785	24.5	4"
EAW-VD9108ZJ247I6-525AXSP06	-	356.7	274.2	307.3	588.3	-	354.5	273.3	305.8	583	545	16.6	4"	436	13.3	3"	654	23.4	4"
EAW-VD9108ZJ247I6-425AXSP06	207.9	324.7	248.4	279.2	543.3	208.1	323.2	247.8	278	539	436	18.4	3"	349	12.1	3"	523	22.5	4"
EAW-VD9110ZJ247I6-625AXSP06	316.3	477.6	370.9	413.2	775.6	315.8	473.8	369	410.9	767.8	654	20.7	4"	523	13.7	4"	785	29.1	4"
EAW-VD9110ZJ247I6-525AXSP04	-	436.4	-	375.4	725.4	-	435	-	-	719.9	812	16	4"	649	10.5	4"	974	18.4	(2) 4"
EAW-VD9110ZJ247I6-425AXSP04	-	399.1	303.2	342.3	670.8	-	397.5	303.1	341.4	665.5	654	14.7	4"	523	9.7	4"	785	20.6	4"
EAW-VD9112ZJ247I6-625AXSP04	-	564.1	-	487.6	921.3	-	561.1	-	485.1	913.1	981	15.8	(2) 4"	785	13.1	4"	1177	22.1	(2) 4"
EAW-VD9112ZJ247I6-525AXSP04	-	530.1	407.7	457	877	-	527.5	406.4	454.8	869.2	812	18.2	4"	649	12	4"	974	21.5	(2) 4"
EAW-VD9112ZJ247I6-425AXSP04	309.8	484.9	370.1	416.2	810.5	310.1	482	369.2	415	804.1	654	16.9	4"	523	11.1	4"	785	23.7	4"
EAW-VD9114ZJ247I6-625AXSP04	-	663.8	515.2	574	1079.7	-	659.4	512.5	570.9	1068.9	981	18	(2) 4"	785	14.6	4"	1177	25.2	(2) 4"
EAW-VD9114ZJ247I6-525AXSP04	406.6	624.3	481.2	538.5	1027	406.4	620.4	479	535.1	1017.7	812	20.4	4"	649	13.5	4"	974	24.6	(2) 4"
EAW-VD9114ZJ247I6-425AXSP02	-	-	-	-	909	-	-	-	-	903.6	1308	10.8	(2) 4"	1046	7.1	(2) 4"	1570	15.2	(2) 4"
EAW-VD9116ZJ247I6-625AXSP02	-	-	-	-	1197.6	-	-	-	-	1188.7	1962	11.9	(3) 4"	1570	9.8	(2) 4"	2354	16.7	(3) 4"
EAW-VD9116ZJ247I6-525AXSP02	-	-	-	-	1139	-	-	-	-	1130.5	1635	13.3	(2) 4"	1308	8.7	(2) 4"	1962	15.6	(3) 4"
EAW-VD9116ZJ247I6-425AXSP02	-	615.1	-	-	1046.3	-	614.8	-	-	1040	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD9118ZJ247I6-625AXSP02	-	-	-	-	1353.6	-	-	-	-	1343.4	1962	13	(3) 4"	1570	10.6	(2) 4"	2354	18.3	(3) 4"
EAW-VD9118ZJ247I6-525AXSP02	-	770.6	-	-	1287.9	-	768.3	-	-	1278.2	1635	14.4	(2) 4"	1308	9.5	(2) 4"	1962	17.2	(3) 4"
EAW-VD9118ZJ247I6-425AXSP02	-	699.7	-	-	1183.8	-	698.1	-	-	1176.6	1308	13	(2) 4"	1046	8.6	(2) 4"	1570	18.3	(2) 4"
EAW-VD9102PA247I6-625AXSP16	-	-	-	-	123	-	-	-	-	122.7	182	15.3	2"	145	10.1	2"	218	21.5	2"
EAW-VD9102PA247I6-525AXSP16	-	68.2	-	-	115.7	-	68.4	-	-	115.5	145	14.2	2"	116	11.6	1-1/2"	174	20	2"
EAW-VD9102PA247I6-425AXSP16	-	63.8	-	-	109.2	-	64	-	-	109.1	121	16.1	1-1/2"	97	10.6	1-1/2"	145	19.1	2"
EAW-VD9104PA247I6-625AXSP12	-	151.7	116.8	130.7	250.1	-	151.5	117	130.8	248.9	242	16.2	3"	194	13.5	2"	291	22.8	3"
EAW-VD9104PA247I6-525AXSP12	90.1	141	107.7	121.1	235.4	90.7	140.8	108	121.2	234.4	194	18.6	2"	155	12.3	2"	232	26.2	2"
EAW-VD9104PA247I6-425AXSP08	-	126.9	-	-	217.8	-	127.4	-	-	217.3	242	11.1	3"	194	10.1	2"	291	15.6	3"
EAW-VD9106PA247I6-625AXSP08	-	226.9	174.7	195.6	374.2	-	226.7	175.1	195.7	372.5	363	16.4	3"	291	10.8	3"	436	23.1	3"
EAW-VD9106PA247I6-525AXSP08	-	215.4	164.7	185.3	359.7	-	215.2	165	185.4	357.7	303	15.7	3"	242	10.4	3"	363	22.1	3"
EAW-VD9106PA247I6-425AXSP08	124.6	197.2	149.7	168.9	333.1	125.6	197.1	150.3	169.1	331.8	242	15.1	3"	194	12.8	2"	291	21.2	3"
EAW-VD9108PA247I6-625AXSP06	-	301.8	232.3	260.4	497.8	-	301.6	232.8	260.5	496.1	484	17.7	3"	388	11.6	3"	581	20.9	4"
EAW-VD9108PA247I6-525AXSP06	-	285.2	217.8	244.8	475.8	-	284.9	218.3	245.3	473.8	400	16.4	3"	320	10.8	3"	480	23	3"
EAW-VD9108PA247I6-425AXSP06	163	258.1	195.9	221.2	436.9	164	258.1	196.4	221.6	435.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD9110PA247I6-625AXSP06	250.5	382.6	295.3	330.4	626.7	251.2	381.8	295.4	330.1	623.8	484	20.7	3"	388	13.6	3"	581	25.1	4"
EAW-VD9110PA247I6-525AXSP04	-	351.4	-	301.4	590.8	-	351.6	-	302	588.4	606	13.1	4"	484	11.4	3"	727	18.5	4"
EAW-VD9110PA247I6-425AXSP04	-	321	242.6	274.6	546.1	-	321.6	243.7	275.6	544.8	484	15.1	3"	388	9.9	3"	581	17.4	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9112PA247I6-625AXSP04	-	450.9	346.4	388.5	744	-	450.6	347.2	388.7	740.6	727	16	4"	581	10.6	4"	872	22.6	4"
EAW-VD9112PA247I6-525AXSP04	-	427.8	326.7	367.3	713.7	-	427.3	327.5	368	710.7	606	15.1	4"	484	12.7	3"	727	21.2	4"
EAW-VD9112PA247I6-425AXSP04	246.9	391.1	296.6	334.8	660.3	248.4	391	297.8	335.4	658.7	484	17.1	3"	388	11.3	3"	581	20.2	4"
EAW-VD9114PA247I6-625AXSP04	346.6	530.9	409.4	458.2	872.1	347.8	529.7	409.6	457.8	868.1	727	18	4"	581	11.9	4"	872	25.4	4"
EAW-VD9114PA247I6-525AXSP02	-	-	-	-	799.8	-	-	-	-	797.9	1211	9.6	(2) 4"	969	6.3	(2) 4"	1453	13.5	(2) 4"
EAW-VD9114PA247I6-425AXSP02	-	-	-	-	736.8	-	-	-	-	736.6	969	8.8	(2) 4"	775	8.4	4"	1163	12.4	(2) 4"
EAW-VD9116PA247I6-625AXSP02	-	-	-	-	963.5	-	-	-	-	960.5	1453	11.5	(2) 4"	1163	7.6	(2) 4"	1744	16.2	(2) 4"
EAW-VD9116PA247I6-525AXSP02	-	-	-	-	921.6	-	-	-	-	919.3	1211	10.6	(2) 4"	969	7	(2) 4"	1453	14.9	(2) 4"
EAW-VD9116PA247I6-425AXSP02	-	492.8	-	-	848.7	-	494.9	-	-	848.4	969	9.8	(2) 4"	775	9.1	4"	1163	13.8	(2) 4"
EAW-VD9118PA247I6-625AXSP02	-	-	-	-	1089.2	-	-	-	-	1087.1	1453	12.5	(2) 4"	1163	8.2	(2) 4"	1744	17.6	(2) 4"
EAW-VD9118PA247I6-525AXSP02	-	616.8	-	-	1042.4	-	618.3	-	-	1039.7	1211	11.6	(2) 4"	969	7.6	(2) 4"	1453	16.3	(2) 4"
EAW-VD9118PA247I6-425AXSP02	-	562.2	-	479.1	962.2	-	563.5	-	482	960.3	969	10.8	(2) 4"	775	9.7	4"	1163	15.2	(2) 4"
EAW-VD9120PA247I6-625AXSP02	-	731.1	-	-	1216.2	-	731.8	-	-	1212.3	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD9120PA247I6-525AXSP02	-	691.4	-	592.4	1164.5	-	692	-	594.8	1161.4	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD9120PA247I6-425AXSP02	-	630.1	476.2	538.3	1074.1	-	631.5	478.4	540.5	1071.8	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD9102PJ247I6-625AXSP16	-	-	-	-	131.5	-	-	-	-	130.9	182	16.2	2"	145	10.7	2"	218	22.8	2"
EAW-VD9102PJ247I6-525AXSP16	-	73.2	-	-	123.5	-	73.3	-	-	123	145	15.1	2"	116	12.2	1-1/2"	174	21.2	2"
EAW-VD9102PJ247I6-425AXSP16	-	68.3	-	58.4	116.5	-	68.4	-	58.6	116	121	17	1-1/2"	97	11.2	1-1/2"	145	20.4	2"
EAW-VD9104PJ247I6-625AXSP12	-	162.6	125.5	140.3	266.8	-	162.2	125.5	140.1	265.1	242	17.6	3"	194	14.4	2"	291	24.6	3"
EAW-VD9104PJ247I6-525AXSP12	97.2	150.7	115.6	129.7	250.9	97.4	150.4	115.6	129.6	249.3	194	19.9	2"	155	13.1	2"	232	28	2"
EAW-VD9104PJ247I6-425AXSP08	-	136.2	-	116.3	232	-	136.2	-	116.7	231	242	12	3"	194	10.7	2"	291	16.9	3"
EAW-VD9106PJ247I6-625AXSP08	-	243.4	187.9	210	399.3	-	242.7	187.7	209.6	396.7	363	17.8	3"	291	11.7	3"	436	24.9	3"
EAW-VD9106PJ247I6-525AXSP08	148.6	230.6	176.7	198.4	382.7	149.2	229.7	176.8	198.2	380.2	303	17	3"	242	11.3	3"	363	23.9	3"
EAW-VD9106PJ247I6-425AXSP06	-	202.7	153.4	173.5	344.3	-	202.7	153.8	173.8	342.9	315	13.3	3"	252	8.8	3"	378	18.7	3"
EAW-VD9108PJ247I6-625AXSP06	-	323.7	249.9	279.6	531.8	-	322.8	249.6	278.8	528.4	484	19	3"	388	12.5	3"	581	22.8	4"
EAW-VD9108PJ247I6-525AXSP06	196.6	304.9	233.8	262.5	506.4	197.3	304.2	233.7	262.3	503.7	400	17.7	3"	320	11.7	3"	480	24.9	3"
EAW-VD9108PJ247I6-425AXSP04	-	269.8	-	230.5	460.5	-	270.2	-	231.3	458.6	484	14	3"	388	9.2	3"	581	15.8	4"
EAW-VD9110PJ247I6-625AXSP04	-	398.4	-	342.9	657.7	-	397.4	-	342.9	654.3	727	15.2	4"	581	10	4"	872	21.3	4"
EAW-VD9110PJ247I6-525AXSP04	-	376.3	287.7	323.3	628.9	-	376	288.1	323.5	626.4	606	14.2	4"	484	12.2	3"	727	20	4"
EAW-VD9110PJ247I6-425AXSP04	-	343.9	260.9	294.3	581.6	-	343.3	261.4	294.7	579.2	484	16.2	3"	388	10.7	3"	581	18.9	4"
EAW-VD9112PJ247I6-625AXSP04	-	483.6	372.8	417.1	793.9	-	482.3	372.9	416.5	789.8	727	17.4	4"	581	11.4	4"	872	24.4	4"
EAW-VD9112PJ247I6-525AXSP04	294.8	457.4	350.7	393.8	760.6	296	456.3	350.5	393.4	755.5	606	16.4	4"	484	13.6	3"	727	23.1	4"
EAW-VD9112PJ247I6-425AXSP02	-	-	-	-	667.1	-	-	-	-	665.7	969	8.5	(2) 4"	775	8.2	4"	1163	11.9	(2) 4"
EAW-VD9114PJ247I6-625AXSP04	373.1	568.6	439.7	491.2	930.6	374	567	439.2	489.8	924.6	727	19.6	4"	581	12.9	4"	872	27.5	4"
EAW-VD9114PJ247I6-525AXSP02	-	-	-	-	854.2	-	-	-	-	851.1	1211	10.4	(2) 4"	969	6.8	(2) 4"	1453	14.6	(2) 4"
EAW-VD9114PJ247I6-425AXSP02	-	457.1	-	-	786.6	-	458.2	-	-	784.9	969	9.6	(2) 4"	775	8.9	4"	1163	13.5	(2) 4"
EAW-VD9116PJ247I6-625AXSP02	-	-	-	-	1029.8	-	-	-	-	1026	1453	12.4	(2) 4"	1163	8.1	(2) 4"	1744	17.5	(2) 4"
EAW-VD9116PJ247I6-525AXSP02	-	581.5	-	-	982.7	-	583.1	-	-	979.1	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD9116PJ247I6-425AXSP02	-	529.6	-	451.9	905.9	-	530.7	-	453.8	902.4	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD9118PJ247I6-625AXSP02	-	701.4	-	-	1165.6	-	700.8	-	-	1159.7	1453	13.5	(2) 4"	1163	8.9	(2) 4"	1744	19	(2) 4"
EAW-VD9118PJ247I6-525AXSP02	-	662	-	566.9	1111.5	-	661.7	-	568.5	1107.3	1211	12.6	(2) 4"	969	8.3	(2) 4"	1453	17.7	(2) 4"
EAW-VD9118PJ247I6-425AXSP02	-	602.9	455	514.9	1025.3	-	603	457.1	515.9	1021.2	969	11.8	(2) 4"	775	10.4	4"	1163	16.6	(2) 4"
EAW-VD91S1MA247I6-625AXSP16	-	-	-	-	70.7	-	-	-	-	70.3	109	15.9	1-1/2"	87	10.5	1-1/2"	131	22.4	1-1/2"
EAW-VD91S1MA247I6-525AXSP16	-	-	-	-	67.4	-	-	-	-	67	97	14.6	1-1/2"	78	9.6	1-1/2"	116	20.5	1-1/2"
EAW-VD91S1MA247I6-425AXSP16	-	36.5	-	-	62.2	-	36.5	-	-	61.8	73	14.3	1-1/2"	58	9.5	1-1/2"	87	20.1	1-1/2"
EAW-VD91S2MA247I6-625AXSP12	-	87.9	-	75.9	144.3	-	87.7	-	75.7	143.1	157	17.3	2"	126	13.9	1-1/2"	189	24.3	2"
EAW-VD91S2MA247I6-525AXSP12	-	83.6	64.2	72	138.4	-	83.2	64.1	71.8	137.4	121	20	1-1/2"	97	13.2	1-1/2"	145	24.9	2"
EAW-VD91S2MA247I6-425AXSP08	-	73	-	-	124.8	-	73.1	-	-	124.2	157	12.2	2"	126	10.5	1-1/2"	189	17.2	2"
EAW-VD91S3MA247I6-625AXSP08	-	130.1	-	112.3	213.9	-	129.7	-	112.1	212.5	230	18.6	2"	184	12.3	2"	276	21	3"
EAW-VD91S3MA247I6-525AXSP08	-	123.5	94.6	106.2	205.1	-	123	94.5	106	203.5	194	17.3	2"	155	11.4	2"	232	24.4	2"
EAW-VD91S3MA247I6-425AXSP08	-	113.4	86.3	97.3	190.7	-	113.2	86.4	97.1	189.5	157	16.2	2"	126	13.2	1-1/2"	189	22.8	2"
EAW-VD91S4MA247I6-625AXSP08	116.1	176.3	136.6	152.5	287.6	116.2	175.3	136.2	151.8	285.3	230	22.6	2"	184	14.9	2"	276	26.6	3"
EAW-VD91S4MA247I6-525AXSP06	-	162.9	124.8	140.1	271	-	162.4	124.7	139.9	269	254	14.6	3"	204	12.5	2"	305	20.6	3"
EAW-VD91S4MA247I6-425AXSP06	-	149.1	113.5	127.8	251	-	148.8	113.5	127.8	249.5	206	17.2	2"	165	11.3	2"	247	20	3"
EAW-VD91S5MA247I6-625AXSP06	145.9	221.8	171.6	191.6	362	146	220.5	171.1	191	359.1	315	18.2	3"	252	12	3"	378	25.6	3"
EAW-VD91S5MA247I6-525AXSP04	-	201.6	-	-	337	-	201	-	-	335	388	13.6	3"	310	8.9	3"	465	19.1	3"
EAW-VD91S5MA247I6-425AXSP04	-	184.9	-	158.2	312.8	-	184.5	-	158.4	311	315	12.7	3"	252	8.4	3"	378	17.8	3"
EAW-VD91S6MA247I6-625AXSP04	-	261.5	-	225.7	429.9	-	260.7	-	225	426.5	472	16.8	3"	378	11	3"	567	20	4"
EAW-VD91S6MA247I6-525AXSP04	-	245	187.8	210.8	407.6	-	244.2	187.5	210.4	404.5	388	15.6	3"	310	10.2	3"	465	21.9	3"
EAW-VD91S6MA247I6-425AXSP04	-	225.1	171.1	193.1	378.6	-	224.2	171.1	192.6	375.8	315	14.7	3"	252	9.7	3"	378	20.6	3"
EAW-FD91S1WK320P7-625AXSP16	-	56.2	43.5	48.5	91.9	-	55.8	43.2	48.3	90.8	91	20.6	2"	73	13.6	2"	109	29	2"
EAW-FD91S1WK320P7-525AXSP16	-	51.6	39.6	44.4	85.4	-	51.3	39.5	44.2	84.6	73	19.5	2"	58	15.2	1-1/2"	87	27.4	2"
EAW-FD91S1WK320P7-425AXSP12	-	45.9	-	39.3	77.6	-	45.7	-	39.2	77	79	15.5	2"	63	12.8	1-1/2"	94	21.7	2"
EAW-FD91S2WK320P7-625AXSP08	-	112.1	86.6	96.8	183.1	-	111.1	86.3	96.1	181.2	182	17.8	3"	145	11.7	3"	218	24.9	3"
EAW-FD91S2WK320P7-525AXSP08	-	104.9	80.6	90.4	173.4	-	104.2	80.2	89.9	171.7	151	17	3"	121	11.3	3"	182	23.9	3"
EAW-FD91S2WK320P7-425AXSP08	60.6	94.7	72.3	81.3	158.7	60.6	94.1	72.1	81	157.2	121	16.5	3"	97	13.6	2"	145	23.1	3"
EAW-FD91S3WK320P7-625AXSP06	-	168.7	130.8	145.8	275.3	-	167.3	129.9	145	272.1	242	20.7	3"	194	13.6	3"	291	25.1	4"
EAW-FD91S3WK320P7-525AXSP04	-	153.1	-	-	255.9	-	152.3	-	-	253.5	303	13.1	4"	242	11.4	3"	363	18.5	4"
EAW-FD91S3WK320P7-425AXSP04	-	138.1	-	118.2	233.3	-	137.6	-	118	231.6	242	15.1	3"	194	9.9	3"	291	17.4	4"
EAW-FD91S4WK320P7-625AXSP04	-	222.7	172.1	192.4	364.6	-	220.9	171.1	191	360.8	363	17.4	4"	291	11.4	4"	436	24.4	4"
EAW-FD91S4WK320P7-525AXSP04	-	208.3	160	179.2	344.6	-	206.7	159.3	178.3	341.4	303	16.4	4"	242	13.6	3"	363	23.1	4"
EAW-FD91S4WK320P7-425AXSP04	119.9	187.9	143.4	161.4	315.1	120	186.9	142.9	160.7	311.8	242	18.5	3"	194	12.1	3"	291	22	4"
EAW-FD91S5WK320P7-625AXSP04	185.8	281.5	218.3	243.6	458.4	185.2	279.2	216.8	241.6	453	363	20.7	4"	291	13.6	4"	436	29.1	4"
EAW-FD91S5WK320P7-525AXSP02	-	-	-	-	416.7	-	-	-	-	414	606	10.9	(2) 4"	484	7.2	(2) 4"	727	15.4	(2) 4"
EAW-FD91S5WK320P7-425AXSP02	-	-	-	-	379.5	-	-	-	-	376.8	484	10.2	(2) 4"	388	9.3	4"	581	14.3	(2) 4"
EAW-FD91S6WK320P7-625AXSP02	-	-	-	-	535.5	-	-	-	-	530	727	13.5	(2) 4"	581	8.9	(2) 4"	872	19	(2) 4"
EAW-FD91S6WK320P7-525AXSP02	-	301.4	-	-	504.6	-	300.1	-	-	500.7	606	12.6	(2) 4"	484	8.3	(2) 4"	727	17.7	(2) 4"
EAW-FD91S6WK320P7-425AXSP02	-	271	-	232.1	460	-	270.5	-	231.8	456	484	11.8	(2) 4"	388	10.4	4"	581	16.6	(2) 4"
EAW-FD15S1ZB370K4-625AXSP16	-	74.7	57.5	64.4	123	-	74.7	57.7	64.5	122.6	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB370K4-525AXSP16	-	69.7	53.2	59.9	116.3	44.9	69.7	53.4	60	116.1	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB370K4-425AXSP12	-	64.5	-	55.1	109.9	-	64.7	-	55.4	109.7	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB550K4-625AXSP16	-	81.9	62.9	70.5	135.4	-	81.9	63.1	70.7	135	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB550K4-525AXSP16	48.6	76.3	58.2	65.5	128	49	76.5	58.5	65.7	127.7	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB550K4-425AXSP12	-	70.5	53.1	60.2	120.7	-	70.9	53.6	60.6	120.7	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB750K4-625AXSP16	-	86.1	66.1	74.1	142.8	56.2	86.3	66.5	74.5	142.6	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB750K4-525AXSP12	-	79.9	-	68.4	135.3	-	80.4	-	69	135.6	133	13.5	3"	107	12.4	2"	160	19	3"
EAW-FD15S1ZB750K4-425AXSP12	-	74.6	56.1	63.6	127.7	-	75	56.6	64.1	127.8	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB370C5-625AXSP16	-	74.7	57.5	64.4	123	-	74.7	57.7	64.5	122.6	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB370K5-525AXSP16	-	69.7	53.2	59.9	116.3	44.9	69.7	53.4	60	116.1	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB370K5-425AXSP12	-	64.5	-	55.1	109.9	-	64.7	-	55.4	109.7	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB550K5-625AXSP16	-	81.9	62.9	70.5	135.4	-	81.9	63.1	70.7	135	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB550K5-525AXSP16	48.6	76.3	58.2	65.5	128	49	76.5	58.5	65.7	127.7	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB550K5-425AXSP12	-	70.5	53.1	60.2	120.7	-	70.9	53.6	60.6	120.7	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB750K5-625AXSP16	-	86.1	66.1	74.1	142.8	56.2	86.3	66.5	74.5	142.6	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB750K5-525AXSP12	-	79.9	-	68.4	135.3	-	80.4	-	69	135.6	133	13.5	3"	107	12.4	2"	160	19	3"
EAW-FD15S1ZB750K5-425AXSP12	-	74.6	56.1	63.6	127.7	-	75	56.6	64.1	127.8	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB370C4-625AXSP16	-	75.8	58.4	65.4	125	-	76.1	58.7	65.7	124.9	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB370C4-525AXSP16	45.6	71.3	54.5	61.3	119.2	46	71.5	54.8	61.5	119.1	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB370C4-425AXSP12	-	66.4	-	56.7	113.3	-	66.7	50.4	57.1	113.3	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB550C4-625AXSP16	-	85	65.2	73.2	140.8	-	85.3	65.7	73.6	140.7	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB550C4-525AXSP12	-	78.9	-	67.6	133.8	-	79.4	-	68.1	133.8	133	13.5	3"	107	12.4	2"	160	19	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1ZB550C4-425AXSP12	-	73.7	55.4	62.9	126.3	-	74.1	56	63.3	126.4	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB370C5-625AXSP16	-	75.8	58.4	65.4	125	-	76.1	58.7	65.7	124.9	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB370C5-525AXSP16	45.6	71.3	54.5	61.3	119.2	46	71.5	54.8	61.5	119.1	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB370C5-425AXSP12	-	66.4	-	56.7	113.3	-	66.7	50.4	57.1	113.3	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB550C5-625AXSP16	-	85	65.2	73.2	140.8	-	85.3	65.7	73.6	140.7	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB550C5-525AXSP12	-	78.9	-	67.6	133.8	-	79.4	-	68.1	133.8	133	13.5	3"	107	12.4	2"	160	19	3"
EAW-FD15S1ZB550C5-425AXSP12	-	73.7	55.4	62.9	126.3	-	74.1	56	63.3	126.4	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB370K8-625AXSP16	-	74.7	57.5	64.4	123	-	74.7	57.7	64.5	122.6	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB370K8-525AXSP16	-	69.7	53.2	59.9	116.3	44.9	69.7	53.4	60	116.1	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB370K8-425AXSP12	-	64.5	-	55.1	109.9	-	64.7	-	55.4	109.7	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB550K8-625AXSP16	-	81.9	62.9	70.5	135.4	-	81.9	63.1	70.7	135	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB550K8-525AXSP16	48.6	76.3	58.2	65.5	128	49	76.5	58.5	65.7	127.7	97	19.9	2"	78	13.1	2"	116	28	2"
EAW-FD15S1ZB550K8-425AXSP12	-	70.5	53.1	60.2	120.7	-	70.9	53.6	60.6	120.7	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S1ZB750K8-625AXSP16	-	86.1	66.1	74.1	142.8	56.2	86.3	66.5	74.5	142.6	121	17.4	3"	97	14.4	2"	145	24.4	3"
EAW-FD15S1ZB750K8-525AXSP12	-	79.9	-	68.4	135.3	-	80.4	-	69	135.6	133	13.5	3"	107	12.4	2"	160	19	3"
EAW-FD15S1ZB750K8-425AXSP12	-	74.6	56.1	63.6	127.7	-	75	56.6	64.1	127.8	109	16.8	2"	87	11	2"	131	18.3	3"
EAW-FD15S2ZB370K4-625AXSP08	-	148.8	114.6	128.3	245.4	-	148.9	115	128.5	244.6	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB370K4-525AXSP08	-	141.2	107.9	121.2	235.5	-	141.3	108.3	121.5	234.9	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB370K4-425AXSP08	83.2	131.5	99.9	112.7	222.1	83.8	131.7	100.3	113.1	221.6	164	16.1	3"	131	10.6	3"	196	22.6	3"
EAW-FD15S2ZB550K4-625AXSP08	-	163.1	125.2	140.5	269.8	-	163.5	125.9	141	269.4	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB550K4-525AXSP08	98.6	154.7	117.9	132.7	258.8	99.5	154.8	118.4	133.2	258.6	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB550K4-425AXSP06	-	140.3	105.5	119.6	240	-	140.8	106.4	120.3	239.9	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB750K4-625AXSP08	-	171.8	131.7	147.8	284.6	-	172.2	132.4	148.5	284.6	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB750K4-525AXSP08	103.8	163	124.4	139.9	273.7	104.9	163.6	125.1	140.6	273.7	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB750K4-425AXSP06	-	148.1	111.4	126.3	254.2	-	148.9	112.4	127.3	254.5	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB370K5-625AXSP08	-	148.8	114.6	128.3	245.4	-	148.9	115	128.5	244.6	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB370K5-525AXSP08	-	141.2	107.9	121.2	235.5	-	141.3	108.3	121.5	234.9	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB370K5-425AXSP08	83.2	131.5	99.9	112.7	222.1	83.8	131.7	100.3	113.1	221.6	164	16.1	3"	131	10.6	3"	196	22.6	3"
EAW-FD15S2ZB550K5-625AXSP08	-	163.1	125.2	140.5	269.8	-	163.5	125.9	141	269.4	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB550K5-525AXSP08	98.6	154.7	117.9	132.7	258.8	99.5	154.8	118.4	133.2	258.6	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB550K5-425AXSP06	-	140.3	105.5	119.6	240	-	140.8	106.4	120.3	239.9	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB750K5-625AXSP08	-	171.8	131.7	147.8	284.6	-	172.2	132.4	148.5	284.6	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB750K5-525AXSP08	103.8	163	124.4	139.9	273.7	104.9	163.6	125.1	140.6	273.7	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB750K5-425AXSP06	-	148.1	111.4	126.3	254.2	-	148.9	112.4	127.3	254.5	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB370C4-625AXSP08	-	151.2	116.2	130.3	249.4	-	151.6	117	130.8	249.1	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB370C4-525AXSP08	92.5	144.5	110.3	124.2	241.3	93.3	144.8	110.9	124.6	241	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB370C4-425AXSP06	-	131.9	-	112.7	225.3	-	132.6	-	113.3	225.2	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB550C4-625AXSP08	-	169.4	129.9	145.8	280.5	-	170	130.8	146.5	280.8	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB550C4-525AXSP08	102.7	161.2	122.9	138.4	270.2	103.6	161.8	123.5	139.1	270.2	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB550C4-425AXSP06	-	146.3	110.2	124.9	251	-	147.3	111.1	126	251.2	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB370C5-625AXSP08	-	151.2	116.2	130.3	249.4	-	151.6	117	130.8	249.1	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB370C5-525AXSP08	92.5	144.5	110.3	124.2	241.3	93.3	144.8	110.9	124.6	241	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB370C5-425AXSP06	-	131.9	-	112.7	225.3	-	132.6	-	113.3	225.2	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB550C5-625AXSP08	-	169.4	129.9	145.8	280.5	-	170	130.8	146.5	280.8	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB550C5-525AXSP08	102.7	161.2	122.9	138.4	270.2	103.6	161.8	123.5	139.1	270.2	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB550C5-425AXSP06	-	146.3	110.2	124.9	251	-	147.3	111.1	126	251.2	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB370K8-625AXSP08	-	148.8	114.6	128.3	245.4	-	148.9	115	128.5	244.6	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB370K8-525AXSP08	-	141.2	107.9	121.2	235.5	-	141.3	108.3	121.5	234.9	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB370K8-425AXSP08	83.2	131.5	99.9	112.7	222.1	83.8	131.7	100.3	113.1	221.6	164	16.1	3"	131	10.6	3"	196	22.6	3"
EAW-FD15S2ZB550K8-625AXSP08	-	163.1	125.2	140.5	269.8	-	163.5	125.9	141	269.4	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB550K8-525AXSP08	98.6	154.7	117.9	132.7	258.8	99.5	154.8	118.4	133.2	258.6	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB550K8-425AXSP06	-	140.3	105.5	119.6	240	-	140.8	106.4	120.3	239.9	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S2ZB750K8-625AXSP08	-	171.8	131.7	147.8	284.6	-	172.2	132.4	148.5	284.6	242	18.4	3"	194	12.1	3"	291	21.7	4"
EAW-FD15S2ZB750K8-525AXSP08	103.8	163	124.4	139.9	273.7	104.9	163.6	125.1	140.6	273.7	200	17	3"	160	11.2	3"	240	23.9	3"
EAW-FD15S2ZB750K8-425AXSP06	-	148.1	111.4	126.3	254.2	-	148.9	112.4	127.3	254.5	218	14	3"	174	9.2	3"	262	16.4	4"
EAW-FD15S3ZB370K4-625AXSP06	-	225.8	174	194.7	370.7	-	225.6	174.4	194.8	369.1	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB370K4-525AXSP06	138.8	215.4	165.1	185.2	357.8	139.5	215.2	165.5	185.5	356.4	272	16.8	4"	218	13.4	3"	327	23.6	4"
EAW-FD15S3ZB370K4-425AXSP04	-	191.2	-	163.2	326.3	-	191.9	-	164.1	325.6	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB550K4-625AXSP06	160.8	247.5	190.5	213.4	407.7	161.9	247.4	191	213.6	407	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB550K4-525AXSP04	-	226.5	-	194.1	383.5	-	227.5	-	195.2	383.2	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB550K4-425AXSP04	-	208.9	157	178.1	357.7	-	210.1	158.7	179.5	358.1	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB750K4-625AXSP04	-	251.4	-	-	421.6	-	252.9	-	-	421.6	490	11.4	(2) 4"	392	10.3	4"	589	16.1	(2) 4"
EAW-FD15S3ZB750K4-525AXSP04	-	238.9	-	204.4	405.4	-	240.6	-	206.2	406.1	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB750K4-425AXSP04	-	220.9	165.9	188.4	378.9	-	222.2	167.6	189.8	379.3	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB370K5-625AXSP06	-	225.8	174	194.7	370.7	-	225.6	174.4	194.8	369.1	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB370K5-525AXSP06	138.8	215.4	165.1	185.2	357.8	139.5	215.2	165.5	185.5	356.4	272	16.8	4"	218	13.4	3"	327	23.6	4"
EAW-FD15S3ZB370K5-425AXSP04	-	191.2	-	163.2	326.3	-	191.9	-	164.1	325.6	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB550K5-625AXSP06	160.8	247.5	190.5	213.4	407.7	161.9	247.4	191	213.6	407	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB550K5-525AXSP04	-	226.5	-	194.1	383.5	-	227.5	-	195.2	383.2	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB550K5-425AXSP04	-	208.9	157	178.1	357.7	-	210.1	158.7	179.5	358.1	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB750K5-625AXSP04	-	251.4	-	-	421.6	-	252.9	-	-	421.6	490	11.4	(2) 4"	392	10.3	4"	589	16.1	(2) 4"
EAW-FD15S3ZB750K5-525AXSP04	-	238.9	-	204.4	405.4	-	240.6	-	206.2	406.1	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB750K5-425AXSP04	-	220.9	165.9	188.4	378.9	-	222.2	167.6	189.8	379.3	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB370C4-625AXSP06	-	229.2	176.8	197.6	376.3	-	229.7	177.5	198.3	375.9	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB370C4-525AXSP06	142	220.3	168.9	189.5	366.7	142.9	220.6	169.5	190.1	366.2	272	16.8	4"	218	13.4	3"	327	23.6	4"
EAW-FD15S3ZB370C4-425AXSP04	-	196.8	-	167.8	336.4	-	197.5	-	169	336.3	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB550C4-625AXSP06	166.8	256.8	197.7	221.2	423.9	168.1	257.7	198.7	222.3	423.7	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB550C4-525AXSP04	-	236	-	202	400.3	-	237.6	-	203.7	400.9	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB550C4-425AXSP04	-	218.3	164.1	186.2	374.7	-	219.5	165.6	187.6	375.1	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB370C5-625AXSP06	-	229.2	176.8	197.6	376.3	-	229.7	177.5	198.3	375.9	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB370C5-525AXSP06	142	220.3	168.9	189.5	366.7	142.9	220.6	169.5	190.1	366.2	272	16.8	4"	218	13.4	3"	327	23.6	4"
EAW-FD15S3ZB370C5-425AXSP04	-	196.8	-	167.8	336.4	-	197.5	-	169	336.3	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB550C5-625AXSP06	166.8	256.8	197.7	221.2	423.9	168.1	257.7	198.7	222.3	423.7	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB550C5-525AXSP04	-	236	-	202	400.3	-	237.6	-	203.7	400.9	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB550C5-425AXSP04	-	218.3	164.1	186.2	374.7	-	219.5	165.6	187.6	375.1	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB370K8-625AXSP06	-	225.8	174	194.7	370.7	-	225.6	174.4	194.8	369.1	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB370K8-525AXSP06	138.8	215.4	165.1	185.2	357.8	139.5	215.2	165.5	185.5	356.4	272	16.8	4"	218	13.4	3"	327	23.6	4"
EAW-FD15S3ZB370K8-425AXSP04	-	191.2	-	163.2	326.3	-	191.9	-	164.1	325.6	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB550K8-625AXSP06	160.8	247.5	190.5	213.4	407.7	161.9	247.4	191	213.6	407	327	17.6	4"	262	11.6	4"	392	24.7	4"
EAW-FD15S3ZB550K8-525AXSP04	-	226.5	-	194.1	383.5	-	227.5	-	195.2	383.2	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB550K8-425AXSP04	-	208.9	157	178.1	357.7	-	210.1	158.7	179.5	358.1	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S3ZB750K8-625AXSP04	-	251.4	-	-	421.6	-	252.9	-	-	421.6	490	11.4	(2) 4"	392	10.3	4"	589	16.1	(2) 4"
EAW-FD15S3ZB750K8-525AXSP04	-	238.9	-	204.4	405.4	-	240.6	-	206.2	406.1	406	13.9	4"	325	9.1	4"	487	15.4	(2) 4"
EAW-FD15S3ZB750K8-425AXSP04	-	220.9	165.9	188.4	378.9	-	222.2	167.6	189.8	379.3	327	12.5	4"	262	8.3	4"	392	17.7	4"
EAW-FD15S4ZB370K4-625AXSP04	-	297.3	228.8	256.2	490.2	-	297.5	229.7	256.7	488.7	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB370K4-525AXSP04	-	282.4	215.7	242.4	470.9	-	282.5	216.6	243	469.8	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB370K4-425AXSP04	164.9	260.9	198	223.5	441	166.1	260.9	198.8	224.2	439.4	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB550K4-625AXSP04	-	325.7	250.1	280.6	539	-	326.5	251.4	281.7	538.2	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB550K4-525AXSP04	197.2	309.4	235.9	265.5	518.3	198.7	309.6	236.9	266.5	517.1	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB550K4-425AXSP04	179.8	285.4	216.4	244.2	483.7	181.3	285.9	217.3	245.1	483.4	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB750K4-625AXSP04	-	343.1	263	295.3	568.4	-	344	264.5	296.5	568.5	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S4ZB750K4-525AXSP04	207.5	326	248.4	279.8	547.4	209.7	327.2	250.1	281.2	547.5	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB750K4-425AXSP02	-	-	-	-	483.2	-	-	-	-	484.8	654	9	(2) 4"	523	5.9	(2) 4"	785	12.7	(2) 4"
EAW-FD15S4ZB370K5-625AXSP04	-	297.3	228.8	256.2	490.2	-	297.5	229.7	256.7	488.7	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB370K5-525AXSP04	-	282.4	215.7	242.4	470.9	-	282.5	216.6	243	469.8	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB370K5-425AXSP04	164.9	260.9	198	223.5	441	166.1	260.9	198.8	224.2	439.4	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB550K5-625AXSP04	-	325.7	250.1	280.6	539	-	326.5	251.4	281.7	538.2	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB550K5-525AXSP04	197.2	309.4	235.9	265.5	518.3	198.7	309.6	236.9	266.5	517.1	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB550K5-425AXSP04	179.8	285.4	216.4	244.2	483.7	181.3	285.9	217.3	245.1	483.4	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB750K5-625AXSP04	-	343.1	263	295.3	568.4	-	344	264.5	296.5	568.5	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB750K5-525AXSP04	207.5	326	248.4	279.8	547.4	209.7	327.2	250.1	281.2	547.5	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB750K5-425AXSP02	-	-	-	-	483.2	-	-	-	-	484.8	654	9	(2) 4"	523	5.9	(2) 4"	785	12.7	(2) 4"
EAW-FD15S4ZB370C4-625AXSP04	-	302	232.1	260.2	498.2	-	302.8	233.4	261.2	497.7	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB370C4-525AXSP04	-	289.1	220.7	248.5	482.5	-	289.6	221.8	249.3	482	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB370C4-425AXSP04	169.4	268.7	204	229.9	454	171	269.1	204.8	231.1	453.8	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB550C4-625AXSP04	-	338.3	259.4	291.2	561	-	339.5	261.1	292.7	560.8	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB550C4-525AXSP04	205.1	322.5	245.9	276.4	541.1	207.2	323.5	247.1	278.2	541.1	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB550C4-425AXSP02	-	-	-	-	477.2	-	-	-	-	479.5	654	9	(2) 4"	523	5.9	(2) 4"	785	12.7	(2) 4"
EAW-FD15S4ZB370C5-625AXSP04	-	302	232.1	260.2	498.2	-	302.8	233.4	261.2	497.7	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB370C5-525AXSP04	-	289.1	220.7	248.5	482.5	-	289.6	221.8	249.3	482	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB370C5-425AXSP04	169.4	268.7	204	229.9	454	171	269.1	204.8	231.1	453.8	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB550C5-625AXSP04	-	338.3	259.4	291.2	561	-	339.5	261.1	292.7	560.8	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB550C5-525AXSP04	205.1	322.5	245.9	276.4	541.1	207.2	323.5	247.1	278.2	541.1	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB550C5-425AXSP02	-	-	-	-	477.2	-	-	-	-	479.5	654	9	(2) 4"	523	5.9	(2) 4"	785	12.7	(2) 4"
EAW-FD15S4ZB370K8-625AXSP04	-	297.3	228.8	256.2	490.2	-	297.5	229.7	256.7	488.7	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB370K8-525AXSP04	-	282.4	215.7	242.4	470.9	-	282.5	216.6	243	469.8	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB370K8-425AXSP04	164.9	260.9	198	223.5	441	166.1	260.9	198.8	224.2	439.4	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB550K8-625AXSP04	-	325.7	250.1	280.6	539	-	326.5	251.4	281.7	538.2	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB550K8-525AXSP04	197.2	309.4	235.9	265.5	518.3	198.7	309.6	236.9	266.5	517.1	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB550K8-425AXSP04	179.8	285.4	216.4	244.2	483.7	181.3	285.9	217.3	245.1	483.4	327	15.5	4"	262	10.2	4"	392	21.9	4"
EAW-FD15S4ZB750K8-625AXSP04	-	343.1	263	295.3	568.4	-	344	264.5	296.5	568.5	490	14.4	(2) 4"	392	12.3	4"	589	20.3	(2) 4"
EAW-FD15S4ZB750K8-525AXSP04	207.5	326	248.4	279.8	547.4	209.7	327.2	250.1	281.2	547.5	406	16.9	4"	325	11.1	4"	487	19.6	(2) 4"
EAW-FD15S4ZB750K8-425AXSP02	-	-	-	-	483.2	-	-	-	-	484.8	654	9	(2) 4"	523	5.9	(2) 4"	785	12.7	(2) 4"
EAW-FD15S5ZB370K4-625AXSP04	246.7	376.8	290.9	325	617.1	247.5	376.1	291.5	325.2	615.1	490	17.4	(2) 4"	392	14.2	4"	589	24.5	(2) 4"
EAW-FD15S5ZB370K4-525AXSP02	-	-	-	-	569.4	-	-	-	-	569.7	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB370K4-425AXSP02	-	306.2	-	-	529.1	-	308.1	-	-	529	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB550K4-625AXSP02	-	-	-	-	651.5	-	-	-	-	652.4	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB550K4-525AXSP02	-	-	-	-	626	-	-	-	-	626.5	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB550K4-425AXSP02	-	334.6	-	-	580.3	-	337.4	-	-	580.3	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB750K4-625AXSP02	-	-	-	-	686.8	-	-	-	-	687.9	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB750K4-525AXSP02	-	385.2	-	-	660.6	-	388.7	-	-	662.9	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB750K4-425AXSP02	-	353.5	-	-	614.1	-	356.4	-	303.7	615.1	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB370K5-625AXSP04	246.7	376.8	290.9	325	617.1	247.5	376.1	291.5	325.2	615.1	490	17.4	(2) 4"	392	14.2	4"	589	24.5	(2) 4"
EAW-FD15S5ZB370K5-525AXSP02	-	-	-	-	569.4	-	-	-	-	569.7	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB370K5-425AXSP02	-	306.2	-	-	529.1	-	308.1	-	-	529	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB550K5-625AXSP02	-	-	-	-	651.5	-	-	-	-	652.4	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB550K5-525AXSP02	-	-	-	-	626	-	-	-	-	626.5	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB550K5-425AXSP02	-	334.6	-	-	580.3	-	337.4	-	-	580.3	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB750K5-625AXSP02	-	-	-	-	686.8	-	-	-	-	687.9	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB750K5-525AXSP02	-	385.2	-	-	660.6	-	388.7	-	-	662.9	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB750K5-425AXSP02	-	353.5	-	-	614.1	-	356.4	-	303.7	615.1	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB370K4-625AXSP04	250.2	382.4	295.5	330.2	627.2	251.9	382.9	296.6	331	626.5	490	17.4	(2) 4"	392	14.2	4"	589	24.5	(2) 4"
EAW-FD15S5ZB370C4-525AXSP02	-	-	-	-	583.3	-	-	-	-	584.4	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB370C4-425AXSP02	-	315	-	-	545.3	-	317.5	-	-	546	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB550C4-625AXSP02	-	-	-	-	677.1	-	-	-	-	678.7	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB550C4-525AXSP02	-	380.6	-	-	653.2	-	383.9	-	-	654.3	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB550C4-425AXSP02	-	349.4	-	-	606.5	-	352.8	-	-	608.3	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB370C5-625AXSP04	250.2	382.4	295.5	330.2	627.2	251.9	382.9	296.6	331	626.5	490	17.4	(2) 4"	392	14.2	4"	589	24.5	(2) 4"
EAW-FD15S5ZB370C5-525AXSP02	-	-	-	-	583.3	-	-	-	-	584.4	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB370C5-425AXSP02	-	315	-	-	545.3	-	317.5	-	-	546	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB550C5-625AXSP02	-	-	-	-	677.1	-	-	-	-	678.7	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB550C5-525AXSP02	-	380.6	-	-	653.2	-	383.9	-	-	654.3	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB550C5-425AXSP02	-	349.4	-	-	606.5	-	352.8	-	-	608.3	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB370K8-625AXSP04	246.7	376.8	290.9	325	617.1	247.5	376.1	291.5	325.2	615.1	490	17.4	(2) 4"	392	14.2	4"	589	24.5	(2) 4"
EAW-FD15S5ZB370K8-525AXSP02	-	-	-	-	569.4	-	-	-	-	569.7	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB370K8-425AXSP02	-	306.2	-	-	529.1	-	308.1	-	-	529	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB550K8-625AXSP02	-	-	-	-	651.5	-	-	-	-	652.4	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB550K8-525AXSP02	-	-	-	-	626	-	-	-	-	626.5	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB550K8-425AXSP02	-	334.6	-	-	580.3	-	337.4	-	-	580.3	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S5ZB750K8-625AXSP02	-	-	-	-	686.8	-	-	-	-	687.9	981	10.5	(3) 4"	785	8.9	(2) 4"	1177	14.8	(3) 4"
EAW-FD15S5ZB750K8-525AXSP02	-	385.2	-	-	660.6	-	388.7	-	-	662.9	818	11.9	(2) 4"	654	7.8	(2) 4"	981	13.7	(3) 4"
EAW-FD15S5ZB750K8-425AXSP02	-	353.5	-	-	614.1	-	356.4	-	303.7	615.1	654	10.5	(2) 4"	523	6.9	(2) 4"	785	14.8	(2) 4"
EAW-FD15S6ZB370K4-625AXSP02	-	-	-	-	718.6	-	-	-	-	717.4	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB370K4-525AXSP02	-	408.3	-	-	690.7	-	410	-	-	689.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB370K4-425AXSP02	-	375.2	-	319.9	641.8	-	376.7	-	321.8	640.6	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB370K4-625AXSP02	-	471.1	-	-	789.7	-	473.1	-	-	788.7	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB550K4-525AXSP02	-	447.5	-	382.5	758.6	-	449.5	-	385.4	758	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB550K4-425AXSP02	-	409.7	308	349.5	704.2	-	412.1	310.6	352.3	704.1	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB750K4-625AXSP02	-	495.2	-	-	831.5	-	498.2	-	-	832.8	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB750K4-525AXSP02	-	471.2	-	403.4	801.8	-	474.6	-	406.4	803.3	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB750K4-425AXSP02	-	433	324.8	368.7	744.3	-	435.6	328.3	372.3	745.3	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB370K5-625AXSP02	-	-	-	-	718.6	-	-	-	-	717.4	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB370K5-525AXSP02	-	408.3	-	-	690.7	-	410	-	-	689.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB370K5-425AXSP02	-	375.2	-	319.9	641.8	-	376.7	-	321.8	640.6	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB550K5-625AXSP02	-	471.1	-	-	789.7	-	473.1	-	-	788.7	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB550K5-525AXSP02	-	447.5	-	382.5	758.6	-	449.5	-	385.4	758	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB550K5-425AXSP02	-	409.7	308	349.5	704.2	-	412.1	310.6	352.3	704.1	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB750K5-625AXSP02	-	495.2	-	-	831.5	-	498.2	-	-	832.8	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB750K5-525AXSP02	-	471.2	-	403.4	801.8	-	474.6	-	406.4	803.3	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB750K5-425AXSP02	-	433	324.8	368.7	744.3	-	435.6	328.3	372.3	745.3	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB370C4-625AXSP02	-	-	-	-	729.4	-	-	-	-	730.6	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB370C4-525AXSP02	-	417.9	-	-	707.6	-	420.8	-	-	707.9	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB370C4-425AXSP02	-	386.1	-	329.5	661.5	-	387.7	-	331.4	661.3	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB550C4-625AXSP02	-	488.4	-	-	820.8	-	491.7	-	-	821.7	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB550C4-525AXSP02	-	466.2	-	398.6	791.6	-	468.6	-	402.1	792.9	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB550C4-425AXSP02	-	427.9	321.2	365.2	736.3	-	430.4	324.5	368	737.1	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB370C5-625AXSP02	-	-	-	-	729.4	-	-	-	-	730.6	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB370C5-525AXSP02	-	417.9	-	-	707.6	-	420.8	-	-	707.9	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB370C5-425AXSP02	-	386.1	-	329.5	661.5	-	387.7	-	331.4	661.3	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB550C5-625AXSP02	-	488.4	-	-	820.8	-	491.7	-	-	821.7	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB550C5-525AXSP02	-	466.2	-	398.6	791.6	-	468.6	-	402.1	792.9	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB550C5-425AXSP02	-	427.9	321.2	365.2	736.3	-	430.4	324.5	368	737.1	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S6ZB370K8-625AXSP02	-	-	-	-	718.6	-	-	-	-	717.4	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB370K8-525AXSP02	-	408.3	-	-	690.7	-	410	-	-	689.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB370K8-425AXSP02	-	375.2	-	319.9	641.8	-	376.7	-	321.8	640.6	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB550K8-625AXSP02	-	471.1	-	-	789.7	-	473.1	-	-	788.7	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB550K8-525AXSP02	-	447.5	-	382.5	758.6	-	449.5	-	385.4	758	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB550K8-425AXSP02	-	409.7	308	349.5	704.2	-	412.1	310.6	352.3	704.1	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S6ZB750K8-625AXSP02	-	495.2	-	-	831.5	-	498.2	-	-	832.8	981	12	(3) 4"	785	9.9	(2) 4"	1177	16.9	(3) 4"
EAW-FD15S6ZB750K8-525AXSP02	-	471.2	-	403.4	801.8	-	474.6	-	406.4	803.3	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.8	(3) 4"
EAW-FD15S6ZB750K8-425AXSP02	-	433	324.8	368.7	744.3	-	435.6	328.3	372.3	745.3	654	12	(2) 4"	523	7.9	(2) 4"	785	16.9	(2) 4"
EAW-FD15S1ZK370K4-625AXSP16	-	80.4	62	69.4	131.8	-	80.2	62.1	69.4	131.1	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK370K4-525AXSP16	48.2	74.9	57.4	64.5	124.6	48.5	74.9	57.6	64.4	124.1	97	21.2	2"	78	14	2"	116	29.8	2"
EAW-FD15S1ZK370K4-425AXSP12	-	69.4	52.5	59.4	117.6	-	69.4	52.8	59.5	117.2	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK550K4-625AXSP16	57.7	88.6	68.2	76.4	145.8	58	88.5	68.4	76.4	145.3	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK550K4-525AXSP12	-	82	62.3	70.3	137.9	-	82.1	62.8	70.6	137.6	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK550K4-425AXSP12	-	76.3	57.6	65.2	129.6	-	76.4	58	65.4	129.6	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK750K4-625AXSP12	-	92.4	-	79.4	153.7	-	92.7	-	79.8	153.6	164	15.2	3"	131	10	3"	196	21.3	3"
EAW-FD15S1ZK750K4-525AXSP12	-	86.9	66	74.5	146.4	-	87.3	66.4	74.9	146.4	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK750K4-425AXSP12	50.5	80.9	61.1	69.1	137.9	51.1	81.2	61.5	69.5	137.9	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK370K5-625AXSP16	-	80.4	62	69.4	131.8	-	80.2	62.1	69.4	131.1	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK370K5-525AXSP16	48.2	74.9	57.4	64.5	124.6	48.5	74.9	57.6	64.4	124.1	97	21.2	2"	78	14	2"	116	29.8	2"
EAW-FD15S1ZK370K5-425AXSP12	-	69.4	52.5	59.4	117.6	-	69.4	52.8	59.5	117.2	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK550K5-625AXSP16	57.7	88.6	68.2	76.4	145.8	58	88.5	68.4	76.4	145.3	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK550K5-525AXSP12	-	82	62.3	70.3	137.9	-	82.1	62.8	70.6	137.6	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK550K5-425AXSP12	-	76.3	57.6	65.2	129.6	-	76.4	58	65.4	129.6	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK750K5-625AXSP12	-	92.4	-	79.4	153.7	-	92.7	-	79.8	153.6	164	15.2	3"	131	10	3"	196	21.3	3"
EAW-FD15S1ZK750K5-525AXSP12	-	86.9	66	74.5	146.4	-	87.3	66.4	74.9	146.4	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK750K5-425AXSP12	50.5	80.9	61.1	69.1	137.9	51.1	81.2	61.5	69.5	137.9	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK370C4-625AXSP16	-	82.4	63.6	71.1	135.2	-	82.4	63.8	71.3	134.9	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK370C4-525AXSP12	-	76.9	-	65.9	129	-	77	-	66.2	128.6	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK370C4-425AXSP12	-	71.8	54.3	61.4	121.8	-	71.9	54.6	61.6	121.5	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK550C4-625AXSP16	60.1	92.5	71.3	79.7	152.6	60.6	92.6	71.5	80	152.4	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK550C4-525AXSP12	-	85.9	65.2	73.5	144.7	-	86.1	65.7	74	144.4	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK550C4-425AXSP12	-	79.8	60.3	68.2	135.9	-	80	60.6	68.5	135.7	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK750C4-525AXSP12	-	89.4	67.8	76.5	150.8	-	89.8	68.4	77	150.8	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK750C4-425AXSP12	52	83.4	62.9	71.2	142.5	52.6	83.8	63.4	71.7	142.3	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK370C5-625AXSP16	-	82.4	63.6	71.1	135.2	-	82.4	63.8	71.3	134.9	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK370C5-525AXSP12	-	76.9	-	65.9	129	-	77	-	66.2	128.6	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK370C5-425AXSP12	-	71.8	54.3	61.4	121.8	-	71.9	54.6	61.6	121.5	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK550C5-625AXSP16	60.1	92.5	71.3	79.7	152.6	60.6	92.6	71.5	80	152.4	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK550C5-525AXSP12	-	85.9	65.2	73.5	144.7	-	86.1	65.7	74	144.4	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK550C5-425AXSP12	-	79.8	60.3	68.2	135.9	-	80	60.6	68.5	135.7	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK750C5-525AXSP12	-	89.4	67.8	76.5	150.8	-	89.8	68.4	77	150.8	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK750C5-425AXSP12	52	83.4	62.9	71.2	142.5	52.6	83.8	63.4	71.7	142.3	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK370K8-625AXSP16	-	80.4	62	69.4	131.8	-	80.2	62.1	69.4	131.1	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK370K8-525AXSP16	48.2	74.9	57.4	64.5	124.6	48.5	74.9	57.6	64.4	124.1	97	21.2	2"	78	14	2"	116	29.8	2"
EAW-FD15S1ZK370K8-425AXSP12	-	69.4	52.5	59.4	117.6	-	69.4	52.8	59.5	117.2	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK550K8-625AXSP16	57.7	88.6	68.2	76.4	145.8	58	88.5	68.4	76.4	145.3	121	18.7	3"	97	15.3	2"	145	26.2	3"
EAW-FD15S1ZK550K8-525AXSP12	-	82	62.3	70.3	137.9	-	82.1	62.8	70.6	137.6	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK550K8-425AXSP12	-	76.3	57.6	65.2	129.6	-	76.4	58	65.4	129.6	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S1ZK750K8-625AXSP12	-	92.4	-	79.4	153.7	-	92.7	-	79.8	153.6	164	15.2	3"	131	10	3"	196	21.3	3"
EAW-FD15S1ZK750K8-525AXSP12	-	86.9	66	74.5	146.4	-	87.3	66.4	74.9	146.4	133	14.5	3"	107	13.1	2"	160	20.4	3"
EAW-FD15S1ZK750K8-425AXSP12	50.5	80.9	61.1	69.1	137.9	51.1	81.2	61.5	69.5	137.9	109	17.7	2"	87	11.7	2"	131	19.7	3"
EAW-FD15S2ZK370K4-625AXSP08	-	160.1	123.7	138.3	262.8	-	160	123.7	138.2	261.5	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK370K4-525AXSP08	97.9	151.8	116.4	130.5	252	98.3	151.5	116.5	130.6	250.8	200	18.4	3"	160	12.1	3"	240	25.8	3"
EAW-FD15S2ZK370K4-425AXSP06	-	137.9	104.4	118	233.9	-	138.1	104.8	118.4	233.4	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK550K4-625AXSP08	114.9	176.4	135.9	152.2	290.8	115.4	176.5	136.2	152.4	289.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK550K4-525AXSP06	-	165	-	141.4	277.7	-	165.4	126.3	142.1	277.1	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK550K4-425AXSP06	-	151.5	114.5	129.7	258.1	-	152	115.3	130.2	257.6	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK750K4-625AXSP08	121.3	186.9	143.7	161.1	308.6	122.2	187	144.2	161.6	307.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK750K4-525AXSP06	-	175.1	132.9	150.1	294.9	-	175.6	133.9	150.8	294.7	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK750K4-425AXSP06	-	160.9	121.5	137.5	274.5	101.5	161.5	122.3	138.3	274.4	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK370K5-625AXSP08	-	160.1	123.7	138.3	262.8	-	160	123.7	138.2	261.5	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK370K5-525AXSP08	97.9	151.8	116.4	130.5	252	98.3	151.5	116.5	130.6	250.8	200	18.4	3"	160	12.1	3"	240	25.8	3"
EAW-FD15S2ZK370K5-425AXSP06	-	137.9	104.4	118	233.9	-	138.1	104.8	118.4	233.4	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK550K5-625AXSP08	114.9	176.4	135.9	152.2	290.8	115.4	176.5	136.2	152.4	289.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK550K5-525AXSP06	-	165	-	141.4	277.7	-	165.4	126.3	142.1	277.1	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK550K5-425AXSP06	-	151.5	114.5	129.7	258.1	-	152	115.3	130.2	257.6	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK750K5-625AXSP08	121.3	186.9	143.7	161.1	308.6	122.2	187	144.2	161.6	307.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK750K5-525AXSP06	-	175.1	132.9	150.1	294.9	-	175.6	133.9	150.8	294.7	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK750K5-425AXSP06	-	160.9	121.5	137.5	274.5	101.5	161.5	122.3	138.3	274.4	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK370C4-625AXSP08	-	164.3	126.7	141.7	269.8	-	164.4	127.1	142	268.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK370C4-525AXSP08	100.7	156.4	119.8	134.6	260	101.3	156.4	120.1	134.7	259.4	200	18.4	3"	160	12.1	3"	240	25.8	3"
EAW-FD15S2ZK370C4-425AXSP06	-	142.6	107.8	121.9	242.3	-	142.8	108.6	122.5	241.6	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK550C4-625AXSP08	119.8	184.5	141.9	159	304.5	120.6	184.8	142.6	159.5	303.8	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK550C4-525AXSP06	-	172.9	131.5	148.2	291	-	173.3	132.3	148.9	290.8	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK550C4-425AXSP06	-	158.7	119.7	135.7	270.5	-	159.2	120.6	136.3	270.2	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK750C4-525AXSP06	-	179.8	136.5	154.1	303.7	-	180.7	137.7	155.1	303.7	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK750C4-425AXSP06	103.2	165.7	125.1	141.7	283.1	104.5	166.5	126	142.4	283.3	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK370C5-625AXSP08	-	164.3	126.7	141.7	269.8	-	164.4	127.1	142	268.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK370C5-525AXSP08	100.7	156.4	119.8	134.6	260	101.3	156.4	120.1	134.7	259.4	200	18.4	3"	160	12.1	3"	240	25.8	3"
EAW-FD15S2ZK370C5-425AXSP06	-	142.6	107.8	121.9	242.3	-	142.8	108.6	122.5	241.6	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK550C5-625AXSP08	119.8	184.5	141.9	159	304.5	120.6	184.8	142.6	159.5	303.8	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK550C5-525AXSP06	-	172.9	131.5	148.2	291	-	173.3	132.3	148.9	290.8	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK550C5-425AXSP06	-	158.7	119.7	135.7	270.5	-	159.2	120.6	136.3	270.2	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK750C5-525AXSP06	-	179.8	136.5	154.1	303.7	-	180.7	137.7	155.1	303.7	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK750C5-425AXSP06	103.2	165.7	125.1	141.7	283.1	104.5	166.5	126	142.4	283.3	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK370K8-625AXSP08	-	160.1	123.7	138.3	262.8	-	160	123.7	138.2	261.5	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK370K8-525AXSP08	97.9	151.8	116.4	130.5	252	98.3	151.5	116.5	130.6	250.8	200	18.4	3"	160	12.1	3"	240	25.8	3"
EAW-FD15S2ZK370K8-425AXSP06	-	137.9	104.4	118	233.9	-	138.1	104.8	118.4	233.4	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK550K8-625AXSP08	114.9	176.4	135.9	152.2	290.8	115.4	176.5	136.2	152.4	289.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK550K8-525AXSP06	-	165	-	141.4	277.7	-	165.4	126.3	142.1	277.1	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK550K8-425AXSP06	-	151.5	114.5	129.7	258.1	-	152	115.3	130.2	257.6	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S2ZK750K8-625AXSP08	121.3	186.9	143.7	161.1	308.6	122.2	187	144.2	161.6	307.9	242	19.7	3"	194	13	3"	291	23.6	4"
EAW-FD15S2ZK750K8-525AXSP06	-	175.1	132.9	150.1	294.9	-	175.6	133.9	150.8	294.7	272	13.3	4"	218	11.1	3"	327	18.7	4"
EAW-FD15S2ZK750K8-425AXSP06	-	160.9	121.5	137.5	274.5	101.5	161.5	122.3	138.3	274.4	218	15	3"	174	9.9	3"	262	17.8	4"
EAW-FD15S3ZK370K4-625AXSP06	159.4	242.7	187.6	209.7	396.9	159.8	242.1	187.6	209.5	394.6	327	19.1	4"	262	12.6	4"	392	26.8	4"
EAW-FD15S3ZK370K4-525AXSP04	-	222.9	-	191.4	374.2	-	223.5	-	191.9	372.9	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK370K4-425AXSP04	-	205.5	155.5	176.1	349.3	-	205.9	156.4	176.4	348	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK550K4-625AXSP04	-	259.1	-	-	431	-	259.7	-	-	430.1	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK550K4-525AXSP04	-	245.3	-	210.2	412.7	-	246	187.7	211.1	411.8	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK550K4-425AXSP04	-	226.1	170.5	193.1	384.7	-	226.5	171.6	193.9	384	327	13.5	4"	262	8.9	4"	392	19.1	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3ZK750K4-625AXSP04	-	274.5	-	235.8	457.2	-	275.4	-	237	456.9	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK750K4-525AXSP04	-	259.9	197.3	222.6	438.7	-	261	198.9	224	438.5	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK750K4-425AXSP04	-	239.6	180.8	204.7	409.1	-	240.6	182	205.9	409.1	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK370K5-625AXSP06	159.4	242.7	187.6	209.7	396.9	159.8	242.1	187.6	209.5	394.6	327	19.1	4"	262	12.6	4"	392	26.8	4"
EAW-FD15S3ZK370K5-525AXSP04	-	222.9	-	191.4	374.2	-	223.5	-	191.9	372.9	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK370K5-425AXSP04	-	205.5	155.5	176.1	349.3	-	205.9	156.4	176.4	348	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK550K5-625AXSP04	-	259.1	-	-	431	-	259.7	-	-	430.1	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK550K5-525AXSP04	-	245.3	-	210.2	412.7	-	246	187.7	211.1	411.8	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK550K5-425AXSP04	-	226.1	170.5	193.1	384.7	-	226.5	171.6	193.9	384	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK750K5-625AXSP04	-	274.5	-	235.8	457.2	-	275.4	-	237	456.9	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK750K5-525AXSP04	-	259.9	197.3	222.6	438.7	-	261	198.9	224	438.5	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK750K5-425AXSP04	-	239.6	180.8	204.7	409.1	-	240.6	182	205.9	409.1	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK370C4-625AXSP06	163.2	248.7	192.4	214.9	407	163.9	248.8	192.7	214.9	406.2	327	19.1	4"	262	12.6	4"	392	26.8	4"
EAW-FD15S3ZK370C4-525AXSP04	-	230	-	197.3	385.9	-	230.3	-	197.9	385.2	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK370C4-425AXSP04	-	212.5	160.8	181.9	361.2	-	213.1	161.7	182.4	360.8	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK550C4-625AXSP04	-	270.9	-	232.9	451.1	-	271.8	-	233.9	450.7	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK550C4-525AXSP04	-	257	194.9	220.2	433	-	257.7	196.5	221.2	432.7	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK550C4-425AXSP04	-	236.4	178.5	202	403.3	-	237.1	179.5	203	402.8	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK750C4-525AXSP04	-	267.3	202.7	228.8	451.1	-	268.6	204.5	230.4	451.8	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK750C4-425AXSP04	153.6	247.1	186.3	210.9	422	155.7	248	187.6	212.3	422.3	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK370C5-625AXSP06	163.2	248.7	192.4	214.9	407	163.9	248.8	192.7	214.9	406.2	327	19.1	4"	262	12.6	4"	392	26.8	4"
EAW-FD15S3ZK370C5-525AXSP04	-	230	-	197.3	385.9	-	230.3	-	197.9	385.2	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK370C5-425AXSP04	-	212.5	160.8	181.9	361.2	-	213.1	161.7	182.4	360.8	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK550C5-625AXSP04	-	270.9	-	232.9	451.1	-	271.8	-	233.9	450.7	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK550C5-525AXSP04	-	257	194.9	220.2	433	-	257.7	196.5	221.2	432.7	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK550C5-425AXSP04	-	236.4	178.5	202	403.3	-	237.1	179.5	203	402.8	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK750C5-525AXSP04	-	267.3	202.7	228.8	451.1	-	268.6	204.5	230.4	451.8	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK750C5-425AXSP04	153.6	247.1	186.3	210.9	422	155.7	248	187.6	212.3	422.3	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK370K8-625AXSP06	159.4	242.7	187.6	209.7	396.9	159.8	242.1	187.6	209.5	394.6	327	19.1	4"	262	12.6	4"	392	26.8	4"
EAW-FD15S3ZK370K8-525AXSP04	-	222.9	-	191.4	374.2	-	223.5	-	191.9	372.9	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK370K8-425AXSP04	-	205.5	155.5	176.1	349.3	-	205.9	156.4	176.4	348	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK550K8-625AXSP04	-	259.1	-	-	431	-	259.7	-	-	430.1	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK550K8-525AXSP04	-	245.3	-	210.2	412.7	-	246	187.7	211.1	411.8	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK550K8-425AXSP04	-	226.1	170.5	193.1	384.7	-	226.5	171.6	193.9	384	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S3ZK750K8-625AXSP04	-	274.5	-	235.8	457.2	-	275.4	-	237	456.9	490	12.4	(2) 4"	392	10.9	4"	589	17.5	(2) 4"
EAW-FD15S3ZK750K8-525AXSP04	-	259.9	197.3	222.6	438.7	-	261	198.9	224	438.5	406	14.9	4"	325	9.8	4"	487	16.8	(2) 4"
EAW-FD15S3ZK750K8-425AXSP04	-	239.6	180.8	204.7	409.1	-	240.6	182	205.9	409.1	327	13.5	4"	262	8.9	4"	392	19.1	4"
EAW-FD15S4ZK370K4-625AXSP04	-	319.9	247	276.3	525.5	-	319.6	247.1	276	522.5	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK370K4-525AXSP04	195.7	303.6	232.8	261	504.1	196.5	303	233.1	261.2	502.3	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK370K4-425AXSP04	178.2	279.9	213.4	240.6	471.3	179.2	279.9	213.8	240.5	469.4	327	16.9	4"	262	11.1	4"	392	23.7	4"
EAW-FD15S4ZK550K4-625AXSP04	229.4	352.4	271.4	303.9	581	230.5	352.6	272	304.5	579	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK550K4-525AXSP04	214.2	333.9	255.5	286.9	556.9	215.5	333.8	256.3	287.6	555	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK550K4-425AXSP02	-	-	-	-	492.5	-	-	-	-	493.3	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK750K4-625AXSP04	242.2	373.4	287.1	321.7	616.4	244	373.6	288	322.7	615.1	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK750K4-525AXSP02	-	-	-	-	564.9	-	-	-	-	566.4	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK750K4-425AXSP02	-	-	-	-	523.1	-	-	-	-	524.2	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK370K5-625AXSP04	-	319.9	247	276.3	525.5	-	319.6	247.1	276	522.5	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK370K5-525AXSP04	195.7	303.6	232.8	261	504.1	196.5	303	233.1	261.2	502.3	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK370K5-425AXSP04	178.2	279.9	213.4	240.6	471.3	179.2	279.9	213.8	240.5	469.4	327	16.9	4"	262	11.1	4"	392	23.7	4"
EAW-FD15S4ZK550K5-625AXSP04	229.4	352.4	271.4	303.9	581	230.5	352.6	272	304.5	579	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK550K5-525AXSP04	214.2	333.9	255.5	286.9	556.9	215.5	333.8	256.3	287.6	555	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK550K5-425AXSP02	-	-	-	-	492.5	-	-	-	-	493.3	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK750K5-625AXSP04	242.2	373.4	287.1	321.7	616.4	244	373.6	288	322.7	615.1	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK750K5-525AXSP02	-	-	-	-	564.9	-	-	-	-	566.4	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK750K5-425AXSP02	-	-	-	-	523.1	-	-	-	-	524.2	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK370C4-625AXSP04	-	328.2	253	283.1	538.9	-	328.4	253.8	283.5	537.8	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK370C4-525AXSP04	201.4	312.8	239.6	269.2	520.6	202.6	312.7	240.3	269.4	518.9	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK370C4-425AXSP02	-	-	-	-	462.9	-	-	-	-	463.3	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK550C4-625AXSP04	239.2	368.6	283.5	317.6	608.2	240.9	369.1	284.7	318.5	606.8	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK550C4-525AXSP02	-	-	-	-	557.6	-	-	-	-	559	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK550C4-425AXSP02	-	-	-	-	515.8	-	-	-	-	517.1	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK750C4-525AXSP02	-	-	-	-	581.5	-	-	-	-	583.4	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK750C4-425AXSP02	-	308.8	-	-	539.2	-	311.9	-	-	541.7	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK370C5-625AXSP04	-	328.2	253	283.1	538.9	-	328.4	253.8	283.5	537.8	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK370C5-525AXSP04	201.4	312.8	239.6	269.2	520.6	202.6	312.7	240.3	269.4	518.9	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK370C5-425AXSP02	-	-	-	-	462.9	-	-	-	-	463.3	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK550C5-625AXSP04	239.2	368.6	283.5	317.6	608.2	240.9	369.1	284.7	318.5	606.8	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK550C5-525AXSP02	-	-	-	-	557.6	-	-	-	-	559	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK550C5-425AXSP02	-	-	-	-	515.8	-	-	-	-	517.1	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK750C5-525AXSP02	-	-	-	-	581.5	-	-	-	-	583.4	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK750C5-425AXSP02	-	308.8	-	-	539.2	-	311.9	-	-	541.7	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK370K8-625AXSP04	-	319.9	247	276.3	525.5	-	319.6	247.1	276	522.5	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK370K8-525AXSP04	195.7	303.6	232.8	261	504.1	196.5	303	233.1	261.2	502.3	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK370K8-425AXSP04	178.2	279.9	213.4	240.6	471.3	179.2	279.9	213.8	240.5	469.4	327	16.9	4"	262	11.1	4"	392	23.7	4"
EAW-FD15S4ZK550K8-625AXSP04	229.4	352.4	271.4	303.9	581	230.5	352.6	272	304.5	579	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK550K8-525AXSP04	214.2	333.9	255.5	286.9	556.9	215.5	333.8	256.3	287.6	555	406	18.2	4"	325	12	4"	487	21.5	(2) 4"
EAW-FD15S4ZK550K8-425AXSP02	-	-	-	-	492.5	-	-	-	-	493.3	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S4ZK750K8-625AXSP04	242.2	373.4	287.1	321.7	616.4	244	373.6	288	322.7	615.1	490	15.8	(2) 4"	392	13.1	4"	589	22.1	(2) 4"
EAW-FD15S4ZK750K8-525AXSP02	-	-	-	-	564.9	-	-	-	-	566.4	818	11.1	(2) 4"	654	7.3	(2) 4"	981	12.5	(3) 4"
EAW-FD15S4ZK750K8-425AXSP02	-	-	-	-	523.1	-	-	-	-	524.2	654	9.7	(2) 4"	523	6.4	(2) 4"	785	13.6	(2) 4"
EAW-FD15S5ZK370K4-625AXSP02	-	-	-	-	636.9	-	-	-	-	635.6	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK370K4-525AXSP02	-	-	-	-	611.5	-	-	-	-	610.3	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK370K4-425AXSP02	-	330.7	-	-	566.7	-	332	-	-	566.5	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK550K4-625AXSP02	-	-	-	-	703.5	-	-	-	-	703.1	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK550K4-525AXSP02	-	396.7	-	-	674.8	-	398.6	-	-	673.6	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK550K4-425AXSP02	-	363.2	-	309.5	624.5	-	364.8	-	311.5	624.4	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK750K4-625AXSP02	-	-	-	-	745.9	-	-	-	-	746.5	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK750K4-525AXSP02	-	420.6	-	-	716.2	-	422.6	-	-	717	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK750K4-425AXSP02	-	385.2	-	327.6	663.6	-	387.1	-	330.4	664.9	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK370K5-625AXSP02	-	-	-	-	636.9	-	-	-	-	635.6	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK370K5-525AXSP02	-	-	-	-	611.5	-	-	-	-	610.3	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK370K5-425AXSP02	-	330.7	-	-	566.7	-	332	-	-	566.5	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK550K5-625AXSP02	-	-	-	-	703.5	-	-	-	-	703.1	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK550K5-525AXSP02	-	396.7	-	-	674.8	-	398.6	-	-	673.6	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK550K5-425AXSP02	-	363.2	-	309.5	624.5	-	364.8	-	311.5	624.4	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK750K5-625AXSP02	-	-	-	-	745.9	-	-	-	-	746.5	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK750K5-525AXSP02	-	420.6	-	-	716.2	-	422.6	-	-	717	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK750K5-425AXSP02	-	385.2	-	327.6	663.6	-	387.1	-	330.4	664.9	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK370C4-625AXSP02	-	-	-	-	653.7	-	-	-	-	653.3	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK370C4-525AXSP02	-	-	-	-	630.5	-	-	-	-	630.2	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK370C4-425AXSP02	-	341.7	-	-	586.7	-	343.6	-	-	586.2	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S5ZK550C4-625AXSP02	-	-	-	-	736.2	-	-	-	-	736.5	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK550C4-525AXSP02	-	415.3	-	-	706.8	-	417.9	-	-	707.5	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK550C4-425AXSP02	-	379.4	-	323.4	654.2	-	381.5	-	325.8	654.7	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK750C4-525AXSP02	-	431.8	-	-	737.3	-	435.5	-	-	738.5	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK750C4-425AXSP02	-	396.4	-	338	685.3	-	399.4	-	340.6	686	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK370C5-625AXSP02	-	-	-	-	653.7	-	-	-	-	653.3	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK370C5-525AXSP02	-	-	-	-	630.5	-	-	-	-	630.2	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK370C5-425AXSP02	-	341.7	-	-	586.7	-	343.6	-	-	586.2	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK550C5-625AXSP02	-	-	-	-	736.2	-	-	-	-	736.5	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK550C5-525AXSP02	-	415.3	-	-	706.8	-	417.9	-	-	707.5	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK550C5-425AXSP02	-	379.4	-	323.4	654.2	-	381.5	-	325.8	654.7	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK750C5-525AXSP02	-	431.8	-	-	737.3	-	435.5	-	-	738.5	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK750C5-425AXSP02	-	396.4	-	338	685.3	-	399.4	-	340.6	686	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK370K8-625AXSP02	-	-	-	-	636.9	-	-	-	-	635.6	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK370K8-525AXSP02	-	-	-	-	611.5	-	-	-	-	610.3	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK370K8-425AXSP02	-	330.7	-	-	566.7	-	332	-	-	566.5	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK550K8-625AXSP02	-	-	-	-	703.5	-	-	-	-	703.1	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK550K8-525AXSP02	-	396.7	-	-	674.8	-	398.6	-	-	673.6	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK550K8-425AXSP02	-	363.2	-	309.5	624.5	-	364.8	-	311.5	624.4	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S5ZK750K8-625AXSP02	-	-	-	-	745.9	-	-	-	-	746.5	981	11.3	(3) 4"	785	9.5	(2) 4"	1177	16	(3) 4"
EAW-FD15S5ZK750K8-525AXSP02	-	420.6	-	-	716.2	-	422.6	-	-	717	818	12.8	(2) 4"	654	8.4	(2) 4"	981	14.9	(3) 4"
EAW-FD15S5ZK750K8-425AXSP02	-	385.2	-	327.6	663.6	-	387.1	-	330.4	664.9	654	11.3	(2) 4"	523	7.5	(2) 4"	785	16	(2) 4"
EAW-FD15S6ZK370K4-625AXSP02	-	464	-	-	770.7	-	465	-	-	768.2	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK370K4-525AXSP02	-	440.7	-	378.1	740.6	-	441.2	-	379.2	738.1	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK370K4-425AXSP02	-	403.6	305.3	345.4	687.3	-	404.4	306.6	346.7	684.9	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK550K4-625AXSP02	-	510.7	-	-	851.5	-	511.9	-	-	849.9	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK550K4-525AXSP02	-	484.1	-	415	816.4	-	485.5	-	417	816	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK550K4-425AXSP02	-	443.6	334.4	379.1	757.7	-	444.6	336.7	380.8	756.3	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK750K4-625AXSP02	-	540.8	-	464.2	903	-	542.7	-	466.5	902.5	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK750K4-525AXSP02	-	513.4	389.2	439.5	867.8	-	515	391.9	442.3	867.5	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK750K4-425AXSP02	-	469.9	354.3	401.6	805.3	-	472	357	404.2	804.2	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK370K5-625AXSP02	-	464	-	-	770.7	-	465	-	-	768.2	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK370K5-525AXSP02	-	440.7	-	378.1	740.6	-	441.2	-	379.2	738.1	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK370K5-425AXSP02	-	403.6	305.3	345.4	687.3	-	404.4	306.6	346.7	684.9	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK550K5-625AXSP02	-	510.7	-	-	851.5	-	511.9	-	-	849.9	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK550K5-525AXSP02	-	484.1	-	415	816.4	-	485.5	-	417	816	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK550K5-425AXSP02	-	443.6	334.4	379.1	757.7	-	444.6	336.7	380.8	756.3	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK750K5-625AXSP02	-	540.8	-	464.2	903	-	542.7	-	466.5	902.5	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK750K5-525AXSP02	-	513.4	389.2	439.5	867.8	-	515	391.9	442.3	867.5	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK750K5-425AXSP02	-	469.9	354.3	401.6	805.3	-	472	357	404.2	804.2	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK370C4-625AXSP02	-	476.1	-	-	791.2	-	477	-	-	789.6	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK370C4-525AXSP02	-	453.9	-	389.2	763.7	-	455.2	-	390.9	762.3	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK370C4-425AXSP02	-	417.2	315	356.6	711.6	-	418.6	317.4	358.5	709.8	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK550C4-625AXSP02	-	533.8	-	458.4	891.2	-	535.6	-	461.2	890.4	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK550C4-525AXSP02	-	506.9	384.5	434.1	856.5	-	509.2	387.1	436.8	856	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK550C4-425AXSP02	-	463.6	349.5	396.4	793.9	-	465.2	352.1	398.5	793.1	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK750C4-525AXSP02	-	527.2	399.8	451.7	892.2	-	530.7	403.4	454.8	893.7	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK750C4-425AXSP02	-	484.5	364.7	413.7	830.4	304.6	487.1	367.9	416.7	829.8	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK370C5-625AXSP02	-	476.1	-	-	791.2	-	477	-	-	789.6	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK370C5-525AXSP02	-	453.9	-	389.2	763.7	-	455.2	-	390.9	762.3	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK370C5-425AXSP02	-	417.2	315	356.6	711.6	-	418.6	317.4	358.5	709.8	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK550C5-625AXSP02	-	533.8	-	458.4	891.2	-	535.6	-	461.2	890.4	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK550C5-525AXSP02	-	506.9	384.5	434.1	856.5	-	509.2	387.1	436.8	856	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK550C5-425AXSP02	-	463.6	349.5	396.4	793.9	-	465.2	352.1	398.5	793.1	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK750C5-525AXSP02	-	527.2	399.8	451.7	892.2	-	530.7	403.4	454.8	893.7	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK750C5-425AXSP02	-	484.5	364.7	413.7	830.4	304.6	487.1	367.9	416.7	829.8	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK370K8-625AXSP02	-	464	-	-	770.7	-	465	-	-	768.2	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK370K8-525AXSP02	-	440.7	-	378.1	740.6	-	441.2	-	379.2	738.1	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK370K8-425AXSP02	-	403.6	305.3	345.4	687.3	-	404.4	306.6	346.7	684.9	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK550K8-625AXSP02	-	510.7	-	-	851.5	-	511.9	-	-	849.9	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK550K8-525AXSP02	-	484.1	-	415	816.4	-	485.5	-	417	816	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK550K8-425AXSP02	-	443.6	334.4	379.1	757.7	-	444.6	336.7	380.8	756.3	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S6ZK750K8-625AXSP02	-	540.8	-	464.2	903	-	542.7	-	466.5	902.5	981	13	(3) 4"	785	10.6	(2) 4"	1177	18.3	(3) 4"
EAW-FD15S6ZK750K8-525AXSP02	-	513.4	389.2	439.5	867.8	-	515	391.9	442.3	867.5	818	14.4	(2) 4"	654	9.5	(2) 4"	981	17.2	(3) 4"
EAW-FD15S6ZK750K8-425AXSP02	-	469.9	354.3	401.6	805.3	-	472	357	404.2	804.2	654	13	(2) 4"	523	8.6	(2) 4"	785	18.3	(2) 4"
EAW-FD15S1PB370K4-625AXSP16	-	69.3	53.4	59.8	114.3	-	69.4	53.6	59.9	114.1	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB370K4-525AXSP16	42.5	66.3	50.7	57	110.7	42.9	66.5	51	57.2	110.5	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB370K4-425AXSP12	-	59.7	45.1	51	102	-	60	45.4	51.4	101.9	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB550K4-625AXSP16	-	75.6	58.1	65.1	125.1	-	75.9	58.4	65.4	125.1	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB550K4-525AXSP16	46.2	72.3	55.2	62.1	121.1	46.6	72.6	55.5	62.4	121	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB550K4-425AXSP12	-	65.1	49	55.5	111.6	-	65.5	49.4	56	111.5	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB750K4-625AXSP16	51.1	79.2	60.7	68.2	131.3	51.6	79.5	61.2	68.6	131.4	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB750K4-525AXSP12	-	74	56.1	63.3	125.5	-	74.6	56.6	63.9	125.6	121	13.3	3"	97	11.6	2"	145	18.6	3"
EAW-FD15S1PB750K4-425AXSP12	-	68.4	51.5	58.4	117.6	-	69	52.1	58.9	117.8	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB370K5-625AXSP16	-	69.3	53.4	59.8	114.3	-	69.4	53.6	59.9	114.1	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB370K5-525AXSP16	42.5	66.3	50.7	57	110.7	42.9	66.5	51	57.2	110.5	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB370K5-425AXSP12	-	59.7	45.1	51	102	-	60	45.4	51.4	101.9	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB550K5-625AXSP16	-	75.6	58.1	65.1	125.1	-	75.9	58.4	65.4	125.1	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB550K5-525AXSP16	46.2	72.3	55.2	62.1	121.1	46.6	72.6	55.5	62.4	121	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB550K5-425AXSP12	-	65.1	49	55.5	111.6	-	65.5	49.4	56	111.5	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB750K5-625AXSP16	51.1	79.2	60.7	68.2	131.3	51.6	79.5	61.2	68.6	131.4	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB750K5-525AXSP12	-	74	56.1	63.3	125.5	-	74.6	56.6	63.9	125.6	121	13.3	3"	97	11.6	2"	145	18.6	3"
EAW-FD15S1PB750K5-425AXSP12	-	68.4	51.5	58.4	117.6	-	69	52.1	58.9	117.8	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB370C4-625AXSP16	-	69.6	53.5	59.9	114.7	-	69.9	53.9	60.3	114.8	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB370C4-525AXSP16	43.1	67.3	51.4	57.8	112.2	43.5	67.5	51.7	58.1	112.3	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB370C4-425AXSP12	-	61.1	46.1	52.2	104.5	-	61.5	46.5	52.6	104.6	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB550C4-525AXSP12	-	73.1	-	62.6	123.7	-	73.6	-	63.1	124.1	121	13.3	3"	97	11.6	2"	145	18.6	3"
EAW-FD15S1PB550C4-425AXSP12	-	67.7	50.9	57.8	116.1	-	68.1	51.5	58.3	116.3	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB370C5-625AXSP16	-	69.6	53.5	59.9	114.7	-	69.9	53.9	60.3	114.8	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB370C5-525AXSP16	43.1	67.3	51.4	57.8	112.2	43.5	67.5	51.7	58.1	112.3	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB370C5-425AXSP12	-	61.1	46.1	52.2	104.5	-	61.5	46.5	52.6	104.6	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB550C5-525AXSP12	-	73.1	-	62.6	123.7	-	73.6	-	63.1	124.1	121	13.3	3"	97	11.6	2"	145	18.6	3"
EAW-FD15S1PB550C5-425AXSP12	-	67.7	50.9	57.8	116.1	-	68.1	51.5	58.3	116.3	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB370K8-625AXSP16	-	69.3	53.4	59.8	114.3	-	69.4	53.6	59.9	114.1	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB370K8-525AXSP16	42.5	66.3	50.7	57	110.7	42.9	66.5	51	57.2	110.5	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB370K8-425AXSP12	-	59.7	45.1	51	102	-	60	45.4	51.4	101.9	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB550K8-625AXSP16	-	75.6	58.1	65.1	125.1	-	75.9	58.4	65.4	125.1	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB550K8-525AXSP16	46.2	72.3	55.2	62.1	121.1	46.6	72.6	55.5	62.4	121	91	19.4	2"	73	12.8	2"	109	27.2	2"
EAW-FD15S1PB550K8-425AXSP12	-	65.1	49	55.5	111.6	-	65.5	49.4	56	111.5	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S1PB750K8-625AXSP16	51.1	79.2	60.7	68.2	131.3	51.6	79.5	61.2	68.6	131.4	109	20.7	2"	87	13.7	2"	131	24	3"
EAW-FD15S1PB750K8-525AXSP12	-	74	56.1	63.3	125.5	-	74.6	56.6	63.9	125.6	121	13.3	3"	97	11.6	2"	145	18.6	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1PB750K8-425AXSP12	-	68.4	51.5	58.4	117.6	-	69	52.1	58.9	117.8	97	15.7	2"	78	10.4	2"	116	22.1	2"
EAW-FD15S2PB370K4-625AXSP08	-	138.3	106.3	119.1	228.1	-	138.3	106.8	119.5	227.4	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB370K4-525AXSP08	84.6	132.3	101	113.5	220.6	85.3	132.4	101.4	114	220.2	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB370K4-425AXSP06	-	118.8	-	101.5	203.1	-	119.2	90.3	102	202.9	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB550K4-625AXSP08	-	150.8	115.8	129.7	249.6	-	151.1	116.4	130.4	249.2	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB550K4-525AXSP08	91.9	144.1	109.9	123.7	241.2	92.7	144.5	110.5	124.2	241	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB550K4-425AXSP06	-	129.3	97.3	110.4	221.8	-	130	98.2	111.2	222	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB750K4-625AXSP08	101.8	157.8	121.1	135.8	261.9	102.8	158.4	121.8	136.5	261.9	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB750K4-525AXSP06	-	147.3	-	126	249.6	-	148.2	112.5	127	250.2	242	14.8	3"	194	9.7	3"	291	16.8	4"
EAW-FD15S2PB750K4-425AXSP06	-	136.1	102.2	115.9	233.6	-	137.2	103.4	117.1	234.5	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB370K5-625AXSP08	-	138.3	106.3	119.1	228.1	-	138.3	106.8	119.5	227.4	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB370K5-525AXSP08	84.6	132.3	101	113.5	220.6	85.3	132.4	101.4	114	220.2	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB370K5-425AXSP06	-	118.8	-	101.5	203.1	-	119.2	90.3	102	202.9	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB550K5-625AXSP08	-	150.8	115.8	129.7	249.6	-	151.1	116.4	130.4	249.2	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB550K5-525AXSP08	91.9	144.1	109.9	123.7	241.2	92.7	144.5	110.5	124.2	241	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB550K5-425AXSP06	-	129.3	97.3	110.4	221.8	-	130	98.2	111.2	222	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB750K5-625AXSP08	101.8	157.8	121.1	135.8	261.9	102.8	158.4	121.8	136.5	261.9	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB750K5-525AXSP06	-	147.3	-	126	249.6	-	148.2	112.5	127	250.2	242	14.8	3"	194	9.7	3"	291	16.8	4"
EAW-FD15S2PB750K5-425AXSP06	-	136.1	102.2	115.9	233.6	-	137.2	103.4	117.1	234.5	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB370C4-625AXSP08	-	138.6	106.6	119.4	228.6	-	139.2	107.4	120.1	228.8	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB370C4-525AXSP08	85.7	133.9	102.4	115.1	223.8	86.6	134.5	103	115.8	223.8	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB370C4-425AXSP06	-	121.6	91.4	103.8	207.8	-	122.3	92.4	104.6	208.2	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB550C4-525AXSP06	-	145.3	-	124.3	246.4	-	146.3	-	125.4	246.9	242	14.8	3"	194	9.7	3"	291	16.8	4"
EAW-FD15S2PB550C4-425AXSP06	-	134.5	101.1	114.6	230.8	-	135.5	102.2	115.7	231.5	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB370C5-625AXSP08	-	138.6	106.6	119.4	228.6	-	139.2	107.4	120.1	228.8	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB370C5-525AXSP08	85.7	133.9	102.4	115.1	223.8	86.6	134.5	103	115.8	223.8	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB370C5-425AXSP06	-	121.6	91.4	103.8	207.8	-	122.3	92.4	104.6	208.2	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB550C5-525AXSP06	-	145.3	-	124.3	246.4	-	146.3	-	125.4	246.9	242	14.8	3"	194	9.7	3"	291	16.8	4"
EAW-FD15S2PB550C5-425AXSP06	-	134.5	101.1	114.6	230.8	-	135.5	102.2	115.7	231.5	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB370K8-625AXSP08	-	138.3	106.3	119.1	228.1	-	138.3	106.8	119.5	227.4	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB370K8-525AXSP08	84.6	132.3	101	113.5	220.6	85.3	132.4	101.4	114	220.2	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB370K8-425AXSP06	-	118.8	-	101.5	203.1	-	119.2	90.3	102	202.9	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB550K8-625AXSP08	-	150.8	115.8	129.7	249.6	-	151.1	116.4	130.4	249.2	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB550K8-525AXSP08	91.9	144.1	109.9	123.7	241.2	92.7	144.5	110.5	124.2	241	182	16.5	3"	145	10.9	3"	218	23.2	3"
EAW-FD15S2PB550K8-425AXSP06	-	129.3	97.3	110.4	221.8	-	130	98.2	111.2	222	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S2PB750K8-625AXSP08	101.8	157.8	121.1	135.8	261.9	102.8	158.4	121.8	136.5	261.9	218	17.5	3"	174	11.5	3"	262	21.3	4"
EAW-FD15S2PB750K8-525AXSP06	-	147.3	-	126	249.6	-	148.2	112.5	127	250.2	242	14.8	3"	194	9.7	3"	291	16.8	4"
EAW-FD15S2PB750K8-425AXSP06	-	136.1	102.2	115.9	233.6	-	137.2	103.4	117.1	234.5	194	13.3	3"	155	8.7	3"	232	18.7	3"
EAW-FD15S3PB370K4-625AXSP06	135.7	208.5	160.5	179.7	342.5	136.5	208.6	161.1	180	341.9	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB370K4-525AXSP04	-	192.1	-	-	324.4	-	192.9	-	-	324.2	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB370K4-425AXSP04	-	177	-	151.2	302.8	-	177.9	134.4	152.2	302.6	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB550K4-625AXSP06	147.6	227.1	174.9	196	374.9	148.7	227.6	175.5	196.4	374.7	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB550K4-525AXSP04	-	209.4	-	179	354.9	-	210.4	-	180.4	355.3	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB550K4-425AXSP04	-	193	145	164.6	330.6	-	194	146.5	165.8	330.9	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB750K4-625AXSP04	-	229.7	-	-	385.6	-	231.3	-	-	386	436	14.5	4"	349	9.5	4"	523	15.6	(2) 4"
EAW-FD15S3PB750K4-525AXSP04	-	219.5	-	187.7	372.8	-	220.9	-	189.2	373.3	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB750K4-425AXSP04	-	202.6	152.3	172.9	348.7	-	204.3	154	174.6	349.4	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB370K5-625AXSP06	135.7	208.5	160.5	179.7	342.5	136.5	208.6	161.1	180	341.9	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB370K5-525AXSP04	-	192.1	-	-	324.4	-	192.9	-	-	324.2	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB370K5-425AXSP04	-	177	-	151.2	302.8	-	177.9	134.4	152.2	302.6	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB550K5-625AXSP06	147.6	227.1	174.9	196	374.9	148.7	227.6	175.5	196.4	374.7	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB550K5-525AXSP04	-	209.4	-	179	354.9	-	210.4	-	180.4	355.3	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB550K5-425AXSP04	-	193	145	164.6	330.6	-	194	146.5	165.8	330.9	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB750K5-625AXSP04	-	229.7	-	-	385.6	-	231.3	-	-	386	436	14.5	4"	349	9.5	4"	523	15.6	(2) 4"
EAW-FD15S3PB750K5-525AXSP04	-	219.5	-	187.7	372.8	-	220.9	-	189.2	373.3	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB750K5-425AXSP04	-	202.6	152.3	172.9	348.7	-	204.3	154	174.6	349.4	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB370C4-625AXSP06	136.2	208.9	161.1	180.3	343.7	137.4	209.6	162.1	181.1	344	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB370C4-525AXSP04	-	194.8	-	-	329.1	-	196	-	168.1	329.5	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB370C4-425AXSP04	-	181.1	136.3	154.6	310.2	-	182.2	137.8	155.8	310.3	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB550C4-525AXSP04	-	216.5	-	185.2	367.5	-	218.4	-	187.2	368.8	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB550C4-425AXSP04	-	200.6	150.7	171	344.5	-	201.8	152.2	172.6	345.1	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB370C5-625AXSP06	136.2	208.9	161.1	180.3	343.7	137.4	209.6	162.1	181.1	344	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB370C5-525AXSP04	-	194.8	-	-	329.1	-	196	-	168.1	329.5	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB370C5-425AXSP04	-	181.1	136.3	154.6	310.2	-	182.2	137.8	155.8	310.3	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB550C5-525AXSP04	-	216.5	-	185.2	367.5	-	218.4	-	187.2	368.8	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB550C5-425AXSP04	-	200.6	150.7	171	344.5	-	201.8	152.2	172.6	345.1	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB370K8-625AXSP06	135.7	208.5	160.5	179.7	342.5	136.5	208.6	161.1	180	341.9	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB370K8-525AXSP04	-	192.1	-	-	324.4	-	192.9	-	-	324.2	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB370K8-425AXSP04	-	177	-	151.2	302.8	-	177.9	134.4	152.2	302.6	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB550K8-625AXSP06	147.6	227.1	174.9	196	374.9	148.7	227.6	175.5	196.4	374.7	291	17	4"	232	13.9	3"	349	23.9	4"
EAW-FD15S3PB550K8-525AXSP04	-	209.4	-	179	354.9	-	210.4	-	180.4	355.3	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB550K8-425AXSP04	-	193	145	164.6	330.6	-	194	146.5	165.8	330.9	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S3PB750K8-625AXSP04	-	229.7	-	-	385.6	-	231.3	-	-	386	436	14.5	4"	349	9.5	4"	523	15.6	(2) 4"
EAW-FD15S3PB750K8-525AXSP04	-	219.5	-	187.7	372.8	-	220.9	-	189.2	373.3	363	13.1	4"	291	8.6	4"	436	18.5	4"
EAW-FD15S3PB750K8-425AXSP04	-	202.6	152.3	172.9	348.7	-	204.3	154	174.6	349.4	291	12	4"	232	10.5	3"	349	16.9	4"
EAW-FD15S4PB370K4-625AXSP04	-	274.4	211	236.6	453.5	-	274.9	212.1	237.1	452.6	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB370K4-525AXSP04	-	262.2	200.4	225.3	438.4	169	262.9	201.3	225.9	437.5	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB370K4-425AXSP04	152.5	241.7	183.4	207.1	409.3	154	242.4	184.3	207.7	408.3	291	15	4"	232	12.5	3"	349	21.1	4"
EAW-FD15S4PB550K4-625AXSP04	-	299.3	229.5	257.6	496.2	-	300.3	231	258.5	495.4	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB550K4-525AXSP04	182.2	285.7	217.9	245.4	479.1	183.9	286.5	219.3	246.4	478.9	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB550K4-425AXSP02	-	-	-	-	421.8	-	-	-	-	423.1	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB750K4-625AXSP04	201.8	313.6	240.1	269.7	520.6	203.7	314.8	241.8	271.1	520.5	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB750K4-525AXSP04	190.5	299.6	228.1	257	503.3	192.7	301	229.9	258.5	503.9	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB750K4-425AXSP02	-	-	-	-	443.7	-	-	-	-	446.3	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB370K5-625AXSP04	-	274.4	211	236.6	453.5	-	274.9	212.1	237.1	452.6	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB370K5-525AXSP04	-	262.2	200.4	225.3	438.4	169	262.9	201.3	225.9	437.5	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB370K5-425AXSP04	152.5	241.7	183.4	207.1	409.3	154	242.4	184.3	207.7	408.3	291	15	4"	232	12.5	3"	349	21.1	4"
EAW-FD15S4PB550K5-625AXSP04	-	299.3	229.5	257.6	496.2	-	300.3	231	258.5	495.4	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB550K5-525AXSP04	182.2	285.7	217.9	245.4	479.1	183.9	286.5	219.3	246.4	478.9	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB550K5-425AXSP02	-	-	-	-	421.8	-	-	-	-	423.1	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB750K5-625AXSP04	201.8	313.6	240.1	269.7	520.6	203.7	314.8	241.8	271.1	520.5	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB750K5-525AXSP04	190.5	299.6	228.1	257	503.3	192.7	301	229.9	258.5	503.9	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB750K5-425AXSP02	-	-	-	-	443.7	-	-	-	-	446.3	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB370C4-625AXSP04	-	275.3	211.4	237.1	454.4	-	276.7	213.1	238.6	454.9	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB370C4-525AXSP04	169.7	265.9	202.8	228.1	444.2	171.6	266.7	204.4	229.4	444.7	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB370C4-425AXSP02	-	-	-	-	395.6	-	-	-	-	397.3	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB550C4-525AXSP04	188.3	295.9	225.4	254	496.9	190.3	297.1	227	255.3	497.2	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB550C4-425AXSP02	-	-	-	-	439.2	-	-	-	-	441.6	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB370C5-625AXSP04	-	275.3	211.4	237.1	454.4	-	276.7	213.1	238.6	454.9	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB370C5-525AXSP04	169.7	265.9	202.8	228.1	444.2	171.6	266.7	204.4	229.4	444.7	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB370C5-425AXSP02	-	-	-	-	395.6	-	-	-	-	397.3	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S4PB550C5-525AXSP04	188.3	295.9	225.4	254	496.9	190.3	297.1	227	255.3	497.2	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB550C5-425AXSP02	-	-	-	-	439.2	-	-	-	-	441.6	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB370K8-625AXSP04	-	274.4	211	236.6	453.5	-	274.9	212.1	237.1	452.6	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB370K8-525AXSP04	-	262.2	200.4	225.3	438.4	169	262.9	201.3	225.9	437.5	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB370K8-425AXSP04	152.5	241.7	183.4	207.1	409.3	154	242.4	184.3	207.7	408.3	291	15	4"	232	12.5	3"	349	21.1	4"
EAW-FD15S4PB550K8-625AXSP04	-	299.3	229.5	257.6	496.2	-	300.3	231	258.5	495.4	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB550K8-525AXSP04	182.2	285.7	217.9	245.4	479.1	183.9	286.5	219.3	246.4	478.9	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB550K8-425AXSP02	-	-	-	-	421.8	-	-	-	-	423.1	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S4PB750K8-625AXSP04	201.8	313.6	240.1	269.7	520.6	203.7	314.8	241.8	271.1	520.5	436	17.4	4"	349	11.5	4"	523	19.8	(2) 4"
EAW-FD15S4PB750K8-525AXSP04	190.5	299.6	228.1	257	503.3	192.7	301	229.9	258.5	503.9	363	16.1	4"	291	10.6	4"	436	22.6	4"
EAW-FD15S4PB750K8-425AXSP02	-	-	-	-	443.7	-	-	-	-	446.3	581	8.5	(2) 4"	465	5.6	(2) 4"	698	11.9	(2) 4"
EAW-FD15S5PB370K4-625AXSP04	227.2	347.9	268.3	300.3	570.9	228.5	347.6	269.2	300.4	569.1	436	20.4	4"	349	13.4	4"	523	24	(2) 4"
EAW-FD15S5PB370K4-525AXSP02	-	-	-	-	527.7	-	-	-	-	528.2	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB370K4-425AXSP02	-	283.8	-	-	490.7	-	285.9	-	-	491.3	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB550K4-625AXSP02	-	-	-	-	598.9	-	-	-	-	599.5	872	12.4	(2) 4"	698	8.1	(2) 4"	1046	14	(3) 4"
EAW-FD15S5PB550K4-525AXSP02	-	336.2	-	-	576	-	339	-	-	577.6	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB550K4-425AXSP02	-	308.9	-	-	536	-	311.3	-	-	536.7	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB750K4-625AXSP02	-	-	-	-	628	-	-	-	-	629.7	872	12.4	(2) 4"	698	8.1	(2) 4"	1046	14	(3) 4"
EAW-FD15S5PB750K4-525AXSP02	-	352.7	-	-	605.6	-	355.7	-	-	607.4	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB750K4-425AXSP02	-	324.5	-	275.7	564.1	-	328.1	-	279.3	566.4	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB370K5-625AXSP04	227.2	347.9	268.3	300.3	570.9	228.5	347.6	269.2	300.4	569.1	436	20.4	4"	349	13.4	4"	523	24	(2) 4"
EAW-FD15S5PB370K5-525AXSP02	-	-	-	-	527.7	-	-	-	-	528.2	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB370K5-425AXSP02	-	283.8	-	-	490.7	-	285.9	-	-	491.3	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB550K5-625AXSP02	-	-	-	-	598.9	-	-	-	-	599.5	872	12.4	(2) 4"	698	8.1	(2) 4"	1046	14	(3) 4"
EAW-FD15S5PB550K5-525AXSP02	-	336.2	-	-	576	-	339	-	-	577.6	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB550K5-425AXSP02	-	308.9	-	-	536	-	311.3	-	-	536.7	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB750K5-625AXSP02	-	-	-	-	628	-	-	-	-	629.7	872	12.4	(2) 4"	698	8.1	(2) 4"	1046	14	(3) 4"
EAW-FD15S5PB750K5-525AXSP02	-	352.7	-	-	605.6	-	355.7	-	-	607.4	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB750K5-425AXSP02	-	324.5	-	275.7	564.1	-	328.1	-	279.3	566.4	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB370C4-625AXSP04	228	348.7	269.2	300.9	572.2	229.9	349.8	270.5	302.3	572.7	436	20.4	4"	349	13.4	4"	523	24	(2) 4"
EAW-FD15S5PB370C4-525AXSP02	-	-	-	-	535.3	-	-	-	-	536.8	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB370C4-425AXSP02	-	290.2	-	-	502.6	-	292.8	-	-	503.7	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB550C4-525AXSP02	-	348	-	-	597.1	-	351.8	-	-	599.4	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB550C4-425AXSP02	-	320.9	-	272.7	557.4	-	324.3	-	276.2	560.3	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB370C5-625AXSP04	228	348.7	269.2	300.9	572.2	229.9	349.8	270.5	302.3	572.7	436	20.4	4"	349	13.4	4"	523	24	(2) 4"
EAW-FD15S5PB370C5-525AXSP02	-	-	-	-	535.3	-	-	-	-	536.8	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB370C5-425AXSP02	-	290.2	-	-	502.6	-	292.8	-	-	503.7	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB550C5-525AXSP02	-	348	-	-	597.1	-	351.8	-	-	599.4	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB550C5-425AXSP02	-	320.9	-	272.7	557.4	-	324.3	-	276.2	560.3	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB370K8-625AXSP04	227.2	347.9	268.3	300.3	570.9	228.5	347.6	269.2	300.4	569.1	436	20.4	4"	349	13.4	4"	523	24	(2) 4"
EAW-FD15S5PB370K8-525AXSP02	-	-	-	-	527.7	-	-	-	-	528.2	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB370K8-425AXSP02	-	283.8	-	-	490.7	-	285.9	-	-	491.3	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB550K8-625AXSP02	-	-	-	-	598.9	-	-	-	-	599.5	872	12.4	(2) 4"	698	8.1	(2) 4"	1046	14	(3) 4"
EAW-FD15S5PB550K8-525AXSP02	-	336.2	-	-	576	-	339	-	-	577.6	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB550K8-425AXSP02	-	308.9	-	-	536	-	311.3	-	-	536.7	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-FD15S5PB750K8-625AXSP02	-	-	-	-	628	-	-	-	-	629.7	872	12.4	(2) 4"	698	8.1	(2) 4"	1046	14	(3) 4"
EAW-FD15S5PB750K8-525AXSP02	-	352.7	-	-	605.6	-	355.7	-	-	607.4	727	11.1	(2) 4"	581	7.3	(2) 4"	872	15.6	(2) 4"
EAW-FD15S5PB750K8-425AXSP02	-	324.5	-	275.7	564.1	-	328.1	-	279.3	566.4	581	10	(2) 4"	465	6.5	(2) 4"	698	14	(2) 4"
EAW-DD1504XL017G7-625AXSP08	413.9	640	491.7	551.4	1059.5	414.1	636.3	489.8	549.1	1049.2	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD1504XL017G7-525AXSP06	-	578.5	-	495.2	976.6	-	576.4	-	495.1	969.6	952	13.4	4"	762	8.9	4"	1143	18.9	4"
EAW-DD1508XL017G7-625AXSP04	824	1274.7	979.1	1098.1	2111.1	824.4	1267.6	976.7	1093.4	2093.3	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD1508XL017G7-525AXSP04	750.4	1174.8	896.6	1008.3	1966.8	751.7	1168.6	895.1	1004.5	1949.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD1512XL017G7-625AXSP02	-	1844.4	-	-	3091.4	-	1840	-	-	3070	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD1512XL017G7-525AXSP02	-	1700.5	-	1453.7	2876.9	-	1695.1	-	1454	2856.9	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S1XL045M4-621AXSP08	-	602.3	464.7	520	990.3	-	598.9	463.4	517.7	981	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL045M4-621AXSP04	-	1201.6	925.4	1035.8	1975.9	-	1193.3	923	1031.3	1957.5	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL045M4-621AXSP04	1214.4	1837	1425.2	1589.5	-	1210.3	1824	1417	1578.1	-	1722	22	6"	1377	17.8	4"	2066	30.9	6"
EAW-DD33S1XL045M4-525AXSP08	357.3	556	425.5	478.4	927.5	356.9	552.6	424.3	476.2	918.9	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL045M4-625AXSP08	-	602	463.3	519	991.5	-	597.9	461	516.2	982.3	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL045M4-525AXSP04	710.9	1108.8	848.2	952.5	1850	711.4	1102.1	846	948.1	1832.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL045M4-625AXSP04	-	1199.2	922.7	1033.6	1978.3	-	1191.2	919.3	1028.1	1957.5	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL045M4-525AXSP02	-	1604.8	-	1375.4	2708.3	-	1600.7	-	1374.3	2687.7	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL045M4-625AXSP02	-	1737.2	-	-	2899	-	1728.8	-	-	2872.6	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL037M4-525AXSP08	341.7	530.7	406.5	456.7	883.1	341.9	527.6	404.9	454	874	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL037M4-625AXSP08	-	572.4	441.5	494.1	941.3	-	568.9	439.6	491.1	932	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL037M4-525AXSP04	681.1	1058.3	810.5	910.6	1761.5	680.6	1050.7	807.4	905.3	1743.5	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL037M4-625AXSP04	-	1141.9	879.3	984.2	1878.2	-	1133.6	875.5	978.3	1857.5	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL037M4-525AXSP02	-	1533.3	-	-	2580.4	-	1527.4	-	-	2558	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL037M4-625AXSP02	-	1655.6	-	-	2753.6	-	1648.5	-	-	2730.3	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL030M4-525AXSP08	328.4	509.2	390.4	438.2	844.5	328.4	505.2	388.6	435.4	835.5	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL030M4-625AXSP08	-	547.8	422.7	472.7	898.3	-	543.6	420.7	469.7	888.3	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL030M4-525AXSP04	-	1014.1	778.4	873.7	1684.7	-	1007.7	775	868.3	1666.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL030M4-625AXSP04	-	1091.4	841.9	941.7	1790.4	-	1083.1	839.1	937	1772.4	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL030M4-525AXSP02	-	1470.4	-	-	2469.1	-	1463.9	-	-	2446.7	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL030M4-625AXSP02	-	-	-	-	2629	-	-	-	-	2603.1	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL045N4-525AXSP08	347.5	539.6	413.6	464.1	898.7	347.2	536.4	411.9	462	889.3	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL045N4-625AXSP08	-	584.3	450.3	504.1	961.6	-	580.5	448.1	500.9	951.6	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL045N4-525AXSP04	691.7	1076.2	824.7	925.4	1792.8	691.1	1069.7	821.3	921.2	1773.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL045N4-625AXSP04	-	1164.1	896.8	1004.1	1918.5	-	1156.6	892.5	999	1898.7	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL045N4-525AXSP02	-	1558.6	-	1337.3	2625.6	-	1552.3	-	1334.2	2602.1	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL045N4-625AXSP02	-	1687.2	-	-	2812.2	-	1679.3	-	-	2787.1	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL037N4-525AXSP08	337.7	524.1	401.8	451.2	871.5	337.7	520.5	399.8	448.2	861.9	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL037N4-625AXSP08	-	566.3	437	489	931	-	562.3	434.6	485.5	920.8	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL037N4-525AXSP04	673.3	1045.2	801	899.7	1736.3	672.2	1038.2	797.2	893.7	1719.3	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL037N4-625AXSP04	-	1129.8	870.4	974.1	1855.3	-	1120.3	865.6	967.2	1835.1	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL037N4-525AXSP02	-	1514.6	-	-	2547.2	-	1507.4	-	-	2522.9	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL037N4-625AXSP02	-	1636.1	-	-	2723.6	-	1629.5	-	-	2694.4	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL030N4-525AXSP08	-	492.7	378.3	424.4	815	-	489.1	376.3	421.3	806.7	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL030N4-625AXSP08	-	529.9	409.9	457.6	867.3	-	525.8	407.4	454.7	857.5	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL030N4-525AXSP04	-	982.6	754.4	845	1625.8	-	974.3	750.4	840.2	1609.5	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL030N4-625AXSP04	-	1057.1	816.5	912.9	1730.5	-	1047.8	811.6	906	1711	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL030N4-525AXSP02	-	1423.6	-	-	2386.7	-	1418	-	-	2363.2	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL030N4-625AXSP02	-	-	-	-	2541.7	-	-	-	-	2513.6	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL045M5-525AXSP08	357.3	556	425.5	478.4	927.5	356.9	552.6	424.3	476.2	918.9	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL045M5-625AXSP08	-	602	463.3	519	991.5	-	597.9	461	516.2	982.3	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL045M5-525AXSP04	710.9	1108.8	848.2	952.5	1850	711.4	1102.1	846	948.1	1832.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL045M5-625AXSP04	-	1199.2	922.7	1033.6	1978.3	-	1191.2	919.3	1028.1	1957.5	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL045M5-525AXSP02	-	1604.8	-	1375.4	2708.3	-	1600.7	-	1374.3	2687.7	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL045M5-625AXSP02	-	1737.2	-	-	2899	-	1728.8	-	-	2872.6	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL037M5-525AXSP08	341.7	530.7	406.5	456.7	883.1	341.9	527.6	404.9	454	874	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL037M5-625AXSP08	-	572.4	441.5	494.1	941.3	-	568.9	439.6	491.1	932	855	16.9	4"	684	11.2	4"	1026	23.7	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-DD33S2XL037M5-525AXSP04	681.1	1058.3	810.5	910.6	1761.5	680.6	1050.7	807.4	905.3	1743.5	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL037M5-625AXSP04	-	1141.9	879.3	984.2	1878.2	-	1133.6	875.5	978.3	1857.5	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL037M5-525AXSP02	-	1533.3	-	-	2580.4	-	1527.4	-	-	2558	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL037M5-625AXSP02	-	1655.6	-	-	2753.6	-	1648.5	-	-	2730.3	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL030M5-525AXSP08	328.4	509.2	390.4	438.2	844.5	328.4	505.2	388.6	435.4	835.5	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL030M5-625AXSP08	-	547.8	422.7	472.7	898.3	-	543.6	420.7	469.7	888.3	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL030M5-525AXSP04	-	1014.1	778.4	873.7	1684.7	-	1007.7	775	868.3	1666.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL030M5-625AXSP04	-	1091.4	841.9	941.7	1790.4	-	1083.1	839.1	937	1772.4	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL030M5-525AXSP02	-	1470.4	-	-	2469.1	-	1463.9	-	-	2446.7	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL030M5-625AXSP02	-	-	-	-	2629	-	-	-	-	2603.1	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL045N5-525AXSP08	347.5	539.6	413.6	464.1	898.7	347.2	536.4	411.9	462	889.3	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL045N5-625AXSP08	-	584.3	450.3	504.1	961.6	-	580.5	448.1	500.9	951.6	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL045N5-525AXSP04	691.7	1076.2	824.7	925.4	1792.8	691.1	1069.7	821.3	921.2	1773.9	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL045N5-625AXSP04	-	1164.1	896.8	1004.1	1918.5	-	1156.6	892.5	999	1898.7	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL045N5-525AXSP02	-	1558.6	-	1337.3	2625.6	-	1552.3	-	1334.2	2602.1	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL045N5-625AXSP02	-	1687.2	-	-	2812.2	-	1679.3	-	-	2787.1	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL037N5-525AXSP08	337.7	524.1	401.8	451.2	871.5	337.7	520.5	399.8	448.2	861.9	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL037N5-625AXSP08	-	566.3	437	489	931	-	562.3	434.6	485.5	920.8	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL037N5-525AXSP04	673.3	1045.2	801	899.7	1736.3	672.2	1038.2	797.2	893.7	1719.3	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL037N5-625AXSP04	-	1129.8	870.4	974.1	1855.3	-	1120.3	865.6	967.2	1835.1	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL037N5-525AXSP02	-	1514.6	-	-	2547.2	-	1507.4	-	-	2522.9	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL037N5-625AXSP02	-	1636.1	-	-	2723.6	-	1629.5	-	-	2694.4	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"
EAW-DD33S1XL030N5-525AXSP08	-	492.7	378.3	424.4	815	-	489.1	376.3	421.3	806.7	708	16.4	4"	567	10.9	4"	850	23	4"
EAW-DD33S1XL030N5-625AXSP08	-	529.9	409.9	457.6	867.3	-	525.8	407.4	454.7	857.5	855	16.9	4"	684	11.2	4"	1026	23.7	4"
EAW-DD33S2XL030N5-525AXSP04	-	982.6	754.4	845	1625.8	-	974.3	750.4	840.2	1609.5	1429	18.6	4"	1143	12.2	4"	1714	21.1	6"
EAW-DD33S2XL030N5-625AXSP04	-	1057.1	816.5	912.9	1730.5	-	1047.8	811.6	906	1711	1722	15.4	6"	1377	13.5	4"	2066	21.6	6"
EAW-DD33S3XL030N5-525AXSP02	-	1423.6	-	-	2386.7	-	1418	-	-	2363.2	2870	13.6	6"	2296	8.9	6"	3443	19.1	6"
EAW-DD33S3XL030N5-625AXSP02	-	-	-	-	2541.7	-	-	-	-	2513.6	3443	15	6"	2755	9.8	6"	4132	16.2	(2) 6"

Note: "-" indicates flow rate is outside of unit capability

STD-201RS Dry Table 3a - IP Units - Dry Fluid Coolers (DFC) 8/25/2022

Evapco EAW Line Thermal Performance in USGPM - 30% Propylene Glycol as Process Fluid

Range °F	10	10	15	15	9	10	10	15	15	9	First	First	First	Second	Second	Second	Third	Third	Third
Approach °F	5	10	10	12	18	5	10	10	12	18	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow
Dry Bulb Temperature °F	77	77	77	77	77	95	95	95	95	95	GPM	PSI	Inlet	GPM	PSI	Inlet	GPM	PSI	Inlet
EAW-VD15S1ZB370K4-625AXSP16	-	-	-	-	177.6	-	-	-	-	175.8	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB370K4-525AXSP16	-	97.4	-	-	166.7	-	98.1	-	-	165.3	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB370K4-425AXSP16	-	89.4	-	76	155	-	90	-	76.8	153.8	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB550K4-625AXSP16	-	118.6	-	-	201.2	-	119.3	-	-	199.3	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB550K4-525AXSP16	-	109.3	-	93.2	188.2	-	110.1	-	94.1	186.6	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB550K4-425AXSP16	-	100	74.3	85	174.3	-	100.9	75.6	85.9	173	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB750K4-625AXSP16	-	128.6	-	-	218.8	-	129.6	-	-	217.2	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB750K4-525AXSP16	-	118.6	-	101	204.6	-	119.5	89.9	102	203.1	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB750K4-425AXSP16	-	108.3	80.2	92	189.1	-	109.4	81.7	93	188.1	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB370K5-625AXSP16	-	-	-	-	177.6	-	-	-	-	175.8	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB370K5-525AXSP16	-	97.4	-	-	166.7	-	98.1	-	-	165.3	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB370K5-425AXSP16	-	89.4	-	76	155	-	90	-	76.8	153.8	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB550K5-625AXSP16	-	118.6	-	-	201.2	-	119.3	-	-	199.3	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB550K5-525AXSP16	-	109.3	-	93.2	188.2	-	110.1	-	94.1	186.6	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB550K5-425AXSP16	-	100	74.3	85	174.3	-	100.9	75.6	85.9	173	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB750K5-625AXSP16	-	128.6	-	-	218.8	-	129.6	-	-	217.2	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB750K5-525AXSP16	-	118.6	-	101	204.6	-	119.5	89.9	102	203.1	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB750K5-425AXSP16	-	108.3	80.2	92	189.1	-	109.4	81.7	93	188.1	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB370C4-625AXSP16	-	-	-	-	185.8	-	-	-	-	183.9	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB370C4-525AXSP16	-	101.4	-	-	174.2	-	102.2	-	-	172.5	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB370C4-425AXSP16	-	92.9	-	79	161.4	-	93.6	-	79.8	160.1	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB550C4-625AXSP16	-	124.7	-	-	212	-	125.5	-	-	210.2	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB550C4-525AXSP16	-	114.7	-	97.6	197.7	-	115.4	-	98.6	196.2	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB550C4-425AXSP16	-	104.5	77.4	88.7	182.2	-	105.2	78.8	89.6	180.7	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB750C4-625AXSP16	-	133.7	-	114.2	227.7	-	134.7	-	115.2	225.9	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB750C4-525AXSP16	-	122.8	91.5	104.6	212.3	-	124.1	93.2	105.8	211	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB750C4-425AXSP16	-	112.1	82.9	95.2	195.8	-	113	84.6	96.2	194.8	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB370C5-625AXSP16	-	-	-	-	185.8	-	-	-	-	183.9	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB370C5-525AXSP16	-	101.4	-	-	174.2	-	102.2	-	-	172.5	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB370C5-425AXSP16	-	92.9	-	79	161.4	-	93.6	-	79.8	160.1	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB550C5-625AXSP16	-	124.7	-	-	212	-	125.5	-	-	210.2	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB550C5-525AXSP16	-	114.7	-	97.6	197.7	-	115.4	-	98.6	196.2	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB550C5-425AXSP16	-	104.5	77.4	88.7	182.2	-	105.2	78.8	89.6	180.7	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB750C5-625AXSP16	-	133.7	-	114.2	227.7	-	134.7	-	115.2	225.9	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB750C5-525AXSP16	-	122.8	91.5	104.6	212.3	-	124.1	93.2	105.8	211	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB750C5-425AXSP16	-	112.1	82.9	95.2	195.8	-	113	84.6	96.2	194.8	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB370K8-625AXSP16	-	-	-	-	177.6	-	-	-	-	175.8	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB370K8-525AXSP16	-	97.4	-	-	166.7	-	98.1	-	-	165.3	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB370K8-425AXSP16	-	89.4	-	76	155	-	90	-	76.8	153.8	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB550K8-625AXSP16	-	118.6	-	-	201.2	-	119.3	-	-	199.3	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB550K8-525AXSP16	-	109.3	-	93.2	188.2	-	110.1	-	94.1	186.6	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB550K8-425AXSP16	-	100	74.3	85	174.3	-	100.9	75.6	85.9	173	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S1ZB750K8-625AXSP16	-	128.6	-	-	218.8	-	129.6	-	-	217.2	242	20.1	3"	194	16.4	2"	291	28.2	3"
EAW-VD15S1ZB750K8-525AXSP16	-	118.6	-	101	204.6	-	119.5	89.9	102	203.1	194	22.8	2"	155	15	2"	232	32	2"
EAW-VD15S1ZB750K8-425AXSP16	-	108.3	80.2	92	189.1	-	109.4	81.7	93	188.1	157	21.5	2"	126	17.2	1-1/2"	189	30.2	2"
EAW-VD15S2ZB370K4-625AXSP12	-	221.1	169.9	190.6	363.7	-	220	170	189.9	358.6	327	26.7	3"	262	17.6	3"	392	37.5	3"
EAW-VD15S2ZB370K4-525AXSP08	-	196.6	-	-	336.8	-	198	-	-	333.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB370K4-425AXSP08	-	181.6	-	154.5	314.7	-	183.1	-	156.2	312.2	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB550K4-625AXSP08	-	236.2	-	-	401	-	237.8	-	-	397.3	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB550K4-525AXSP08	-	221.1	-	188.4	380.3	-	222.7	-	190.3	376.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB550K4-425AXSP08	-	203.6	-	173	354.2	-	205.1	153.8	174.7	351.3	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB750K4-625AXSP08	-	256.2	-	-	436.5	-	258.5	-	-	433.3	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB750K4-525AXSP08	-	240	-	204.2	413.6	-	241.8	-	206.5	410.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB750K4-425AXSP08	-	220.4	163.3	187.1	384.4	-	222.3	166.4	189.3	382.3	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB370K5-625AXSP12	-	221.1	169.9	190.6	363.7	-	220	170	189.9	358.6	327	26.7	3"	262	17.6	3"	392	37.5	3"
EAW-VD15S2ZB370K5-525AXSP08	-	196.6	-	-	336.8	-	198	-	-	333.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB370K5-425AXSP08	-	181.6	-	154.5	314.7	-	183.1	-	156.2	312.2	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB550K5-625AXSP08	-	236.2	-	-	401	-	237.8	-	-	397.3	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB550K5-525AXSP08	-	221.1	-	188.4	380.3	-	222.7	-	190.3	376.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB550K5-425AXSP08	-	203.6	-	173	354.2	-	205.1	153.8	174.7	351.3	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB750K5-625AXSP08	-	256.2	-	-	436.5	-	258.5	-	-	433.3	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB750K5-525AXSP08	-	240	-	204.2	413.6	-	241.8	-	206.5	410.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB750K5-425AXSP08	-	220.4	163.3	187.1	384.4	-	222.3	166.4	189.3	382.3	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB370C4-625AXSP08	-	-	-	-	370.7	-	-	-	-	366.9	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB370C4-525AXSP08	-	205.2	-	-	351.5	-	206.4	-	-	348.5	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB370C4-425AXSP08	-	188.8	-	160.4	327.7	-	190.3	-	162.2	325	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB550C4-625AXSP08	-	248.5	-	-	423	-	250.1	-	-	418.9	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB550C4-525AXSP08	-	231.8	-	197.7	399.5	-	233.5	-	199.6	396.4	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB550C4-425AXSP08	-	212.4	157.4	180.5	370.3	-	214.2	160.4	182.3	367.2	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB750C4-625AXSP08	-	266.4	-	227.3	454.4	-	268.3	-	229.8	450.8	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB750C4-525AXSP08	-	248.6	185.2	211.7	429.7	-	251	188.8	214.2	426.5	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB750C4-425AXSP08	-	228.1	168.7	193.5	398	-	230.2	172	195.8	395.8	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB370C5-625AXSP08	-	-	-	-	370.7	-	-	-	-	366.9	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB370C5-525AXSP08	-	205.2	-	-	351.5	-	206.4	-	-	348.5	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB370C5-425AXSP08	-	188.8	-	160.4	327.7	-	190.3	-	162.2	325	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB550C5-625AXSP08	-	248.5	-	-	423	-	250.1	-	-	418.9	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB550C5-525AXSP08	-	231.8	-	197.7	399.5	-	233.5	-	199.6	396.4	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB550C5-425AXSP08	-	212.4	157.4	180.5	370.3	-	214.2	160.4	182.3	367.2	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB750C5-625AXSP08	-	266.4	-	227.3	454.4	-	268.3	-	229.8	450.8	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB750C5-525AXSP08	-	248.6	185.2	211.7	429.7	-	251	188.8	214.2	426.5	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB750C5-425AXSP08	-	228.1	168.7	193.5	398	-	230.2	172	195.8	395.8	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB370K8-625AXSP12	-	221.1	169.9	190.6	363.7	-	220	170	189.9	358.6	327	26.7	3"	262	17.6	3"	392	37.5	3"
EAW-VD15S2ZB370K8-525AXSP08	-	196.6	-	-	336.8	-	198	-	-	333.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB370K8-425AXSP08	-	181.6	-	154.5	314.7	-	183.1	-	156.2	312.2	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB550K8-625AXSP08	-	236.2	-	-	401	-	237.8	-	-	397.3	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB550K8-525AXSP08	-	221.1	-	188.4	380.3	-	222.7	-	190.3	376.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB550K8-425AXSP08	-	203.6	-	173	354.2	-	205.1	153.8	174.7	351.3	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S2ZB750K8-625AXSP08	-	256.2	-	-	436.5	-	258.5	-	-	433.3	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD15S2ZB750K8-525AXSP08	-	240	-	204.2	413.6	-	241.8	-	206.5	410.9	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD15S2ZB750K8-425AXSP08	-	220.4	163.3	187.1	384.4	-	222.3	166.4	189.3	382.3	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD15S3ZB370K4-625AXSP08	-	329.7	252.8	283.7	542.5	-	328.1	253.1	282.8	535	484	27.9	3"	388	18.4	3"	581	34.8	4"
EAW-VD15S3ZB370K4-525AXSP06	-	302.3	-	258.7	512.7	-	303.4	-	260.2	507.5	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB370K4-425AXSP06	-	276.2	206.7	235.6	474.6	-	277.5	209.2	237.3	470.2	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB550K4-625AXSP06	-	361.3	-	309.4	607.8	-	362.1	-	311.1	601.4	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB550K4-525AXSP06	-	340.2	255.5	290.5	579.1	-	341.5	258.6	292.2	573.8	545	19.4	4"	436	15.3	3"	654	27.2	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3ZB550K4-425AXSP06	-	309.4	231.1	263.5	534.3	-	311	234.4	265.5	529.9	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB750K4-625AXSP06	-	392.1	-	335.3	661.8	-	393.8	-	337.8	656	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB750K4-525AXSP06	-	369.1	276.8	315.1	630.1	-	371	280.6	317.4	625.1	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB750K4-425AXSP06	-	335.5	250	285.7	579.9	207.9	337.2	253.7	287.8	575.8	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB370K5-625AXSP08	-	329.7	252.8	283.7	542.5	-	328.1	253.1	282.8	535	484	27.9	3"	388	18.4	3"	581	34.8	4"
EAW-VD15S3ZB370K5-525AXSP06	-	302.3	-	258.7	512.7	-	303.4	-	260.2	507.5	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB370K5-425AXSP06	-	276.2	206.7	235.6	474.6	-	277.5	209.2	237.3	470.2	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB550K5-625AXSP06	-	361.3	-	309.4	607.8	-	362.1	-	311.1	601.4	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB550K5-525AXSP06	-	340.2	255.5	290.5	579.1	-	341.5	258.6	292.2	573.8	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB550K5-425AXSP06	-	309.4	231.1	263.5	534.3	-	311	234.4	265.5	529.9	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB750K5-625AXSP06	-	392.1	-	335.3	661.8	-	393.8	-	337.8	656	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB750K5-525AXSP06	-	369.1	276.8	315.1	630.1	-	371	280.6	317.4	625.1	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB750K5-425AXSP06	-	335.5	250	285.7	579.9	207.9	337.2	253.7	287.8	575.8	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB370C4-625AXSP08	-	344.2	263.6	296.5	568.2	-	342.7	264.1	295.5	560.3	484	27.9	3"	388	18.4	3"	581	34.8	4"
EAW-VD15S3ZB370C4-525AXSP06	-	315.1	-	269.5	535.1	-	316.3	-	271.1	529.7	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB370C4-425AXSP06	-	287.2	214.9	244.7	494.3	-	288.5	217.5	246.4	489.5	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB550C4-625AXSP06	-	380.1	-	325.3	641.2	-	381.4	-	327	634.2	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB550C4-525AXSP06	-	356.9	268	304.9	608.5	-	358.2	271.2	306.7	602.8	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB550C4-425AXSP06	-	323.3	241.4	275.1	558.7	-	324.9	244.5	277.1	553.8	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB750C4-625AXSP06	-	407.1	307.4	348.4	688.9	-	409.3	311.4	351	682.5	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB750C4-525AXSP06	-	383	286.8	326.7	654.7	-	384.7	291	328.8	648.9	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB750C4-425AXSP06	208.1	346.8	258.4	295.5	600.5	214.8	349.2	262.3	297.8	596.3	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB370C5-625AXSP08	-	344.2	263.6	296.5	568.2	-	342.7	264.1	295.5	560.3	484	27.9	3"	388	18.4	3"	581	34.8	4"
EAW-VD15S3ZB370C5-525AXSP06	-	315.1	-	269.5	535.1	-	316.3	-	271.1	529.7	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB370C5-425AXSP06	-	287.2	214.9	244.7	494.3	-	288.5	217.5	246.4	489.5	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB550C5-625AXSP06	-	380.1	-	325.3	641.2	-	381.4	-	327	634.2	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB550C5-525AXSP06	-	356.9	268	304.9	608.5	-	358.2	271.2	306.7	602.8	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB550C5-425AXSP06	-	323.3	241.4	275.1	558.7	-	324.9	244.5	277.1	553.8	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB750C5-625AXSP06	-	407.1	307.4	348.4	688.9	-	409.3	311.4	351	682.5	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB750C5-525AXSP06	-	383	286.8	326.7	654.7	-	384.7	291	328.8	648.9	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB750C5-425AXSP06	208.1	346.8	258.4	295.5	600.5	214.8	349.2	262.3	297.8	596.3	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB370K8-625AXSP08	-	329.7	252.8	283.7	542.5	-	328.1	253.1	282.8	535	484	27.9	3"	388	18.4	3"	581	34.8	4"
EAW-VD15S3ZB370K8-525AXSP06	-	302.3	-	258.7	512.7	-	303.4	-	260.2	507.5	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB370K8-425AXSP06	-	276.2	206.7	235.6	474.6	-	277.5	209.2	237.3	470.2	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB550K8-625AXSP06	-	361.3	-	309.4	607.8	-	362.1	-	311.1	601.4	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB550K8-525AXSP06	-	340.2	255.5	290.5	579.1	-	341.5	258.6	292.2	573.8	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB550K8-425AXSP06	-	309.4	231.1	263.5	534.3	-	311	234.4	265.5	529.9	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S3ZB750K8-625AXSP06	-	392.1	-	335.3	661.8	-	393.8	-	337.8	656	654	20.2	4"	523	13.3	4"	785	28.3	4"
EAW-VD15S3ZB750K8-525AXSP06	-	369.1	276.8	315.1	630.1	-	371	280.6	317.4	625.1	545	19.4	4"	436	15.3	3"	654	27.2	4"
EAW-VD15S3ZB750K8-425AXSP06	-	335.5	250	285.7	579.9	207.9	337.2	253.7	287.8	575.8	436	21.2	3"	349	13.9	3"	523	26.2	4"
EAW-VD15S4ZB370K4-625AXSP06	-	440.6	337.9	379.3	725.8	-	438.5	338.3	378.5	715.7	654	25.4	4"	523	16.8	4"	785	35.6	4"
EAW-VD15S4ZB370K4-525AXSP04	-	392.7	-	-	673.6	-	396	-	-	667.7	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB370K4-425AXSP04	-	359.8	-	305.9	625.2	-	362.9	-	309.3	620.3	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB550K4-625AXSP04	-	471.2	-	-	801	-	474.3	-	-	793.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB550K4-525AXSP04	-	441.5	-	376.3	760.5	-	445.4	-	380	753.8	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB550K4-425AXSP04	-	403.3	-	342.4	702.4	-	406.9	304.5	346.4	697.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB750K4-625AXSP04	-	511.1	-	-	872	-	515.6	-	-	865.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB750K4-525AXSP04	-	479.4	-	407.8	827.2	-	483.7	-	412.5	821.9	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB750K4-425AXSP04	-	436.3	322.8	370.8	763.1	-	441	329.2	375.2	758	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB370K5-625AXSP06	-	440.6	337.9	379.3	725.8	-	438.5	338.3	378.5	715.7	654	25.4	4"	523	16.8	4"	785	35.6	4"
EAW-VD15S4ZB370K5-525AXSP04	-	392.7	-	-	673.6	-	396	-	-	667.7	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB370K5-425AXSP04	-	359.8	-	305.9	625.2	-	362.9	-	309.3	620.3	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB550K5-625AXSP04	-	471.2	-	-	801	-	474.3	-	-	793.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB550K5-525AXSP04	-	441.5	-	376.3	760.5	-	445.4	-	380	753.8	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB550K5-425AXSP04	-	403.3	-	342.4	702.4	-	406.9	304.5	346.4	697.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB750K5-625AXSP04	-	511.1	-	-	872	-	515.6	-	-	865.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB750K5-525AXSP04	-	479.4	-	407.8	827.2	-	483.7	-	412.5	821.9	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB750K5-425AXSP04	-	436.3	322.8	370.8	763.1	-	441	329.2	375.2	758	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB370C4-625AXSP06	-	460.1	352.9	396.3	759.3	-	458	353.5	395	748.8	654	25.4	4"	523	16.8	4"	785	35.6	4"
EAW-VD15S4ZB370C4-525AXSP04	-	409.8	-	-	703	-	412.8	-	-	696.9	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB370C4-425AXSP04	-	374	-	318.2	650	-	377.2	-	321.2	644.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB550C4-625AXSP04	-	495.6	-	-	844.9	-	499.5	-	-	836.9	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB550C4-525AXSP04	-	463.6	-	394.7	798.9	-	467.1	-	398.6	792.7	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB550C4-425AXSP04	-	420.6	311.3	357.3	734.3	-	424.4	317.4	361.4	729.2	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB750C4-625AXSP04	-	531.3	-	-	907.6	-	535.9	-	458.3	900.4	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB750C4-525AXSP04	-	496.5	-	422.7	858.2	-	501.3	376.9	427.8	853	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB750C4-425AXSP04	-	451.6	334.2	383.5	790.1	-	455.9	340.3	388.1	784.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB370C5-625AXSP06	-	460.1	352.9	396.3	759.3	-	458	353.5	395	748.8	654	25.4	4"	523	16.8	4"	785	35.6	4"
EAW-VD15S4ZB370C5-525AXSP04	-	409.8	-	-	703	-	412.8	-	-	696.9	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB370C5-425AXSP04	-	374	-	318.2	650	-	377.2	-	321.2	644.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB550C5-625AXSP04	-	495.6	-	-	844.9	-	499.5	-	-	836.9	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB550C5-525AXSP04	-	463.6	-	394.7	798.9	-	467.1	-	398.6	792.7	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB550C5-425AXSP04	-	420.6	311.3	357.3	734.3	-	424.4	317.4	361.4	729.2	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB750C5-625AXSP04	-	531.3	-	-	907.6	-	535.9	-	458.3	900.4	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB750C5-525AXSP04	-	496.5	-	422.7	858.2	-	501.3	376.9	427.8	853	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB750C5-425AXSP04	-	451.6	334.2	383.5	790.1	-	455.9	340.3	388.1	784.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB370K8-625AXSP06	-	440.6	337.9	379.3	725.8	-	438.5	338.3	378.5	715.7	654	25.4	4"	523	16.8	4"	785	35.6	4"
EAW-VD15S4ZB370K8-525AXSP04	-	392.7	-	-	673.6	-	396	-	-	667.7	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB370K8-425AXSP04	-	359.8	-	305.9	625.2	-	362.9	-	309.3	620.3	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB550K8-625AXSP04	-	471.2	-	-	801	-	474.3	-	-	793.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB550K8-525AXSP04	-	441.5	-	376.3	760.5	-	445.4	-	380	753.8	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB550K8-425AXSP04	-	403.3	-	342.4	702.4	-	406.9	304.5	346.4	697.8	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S4ZB750K8-625AXSP04	-	511.1	-	-	872	-	515.6	-	-	865.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD15S4ZB750K8-525AXSP04	-	479.4	-	407.8	827.2	-	483.7	-	412.5	821.9	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD15S4ZB750K8-425AXSP04	-	436.3	322.8	370.8	763.1	-	441	329.2	375.2	758	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD15S5ZB370K4-625AXSP04	-	538.1	-	462	896.1	-	537.8	-	463	884.7	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB370K4-525AXSP04	-	506.6	382.9	433.7	854.5	-	507	386.1	434.8	844.8	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB370K4-425AXSP04	-	464.6	348.6	396.5	793.2	-	465.3	352.1	397.9	784.7	654	21.3	4"	523	14	4"	785	29.9	4"
EAW-VD15S5ZB550K4-625AXSP04	-	606.7	460.9	520.6	1015.4	-	607.2	464.4	521.9	1003.5	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB550K4-525AXSP04	-	569.4	429.9	487.1	964	-	570	433.7	489.1	954.1	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB550K4-425AXSP02	-	-	-	-	823.1	-	-	-	-	824.9	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB750K4-625AXSP04	-	658.6	499	564.3	1104.4	-	659.6	504.1	566.9	1094.7	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB750K4-525AXSP04	379.7	617.8	465.8	528.3	1048.8	389.4	619.3	469.8	530.6	1039.2	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB750K4-425AXSP02	-	-	-	-	892.5	-	-	-	-	895.8	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB370K5-625AXSP04	-	538.1	-	462	896.1	-	537.8	-	463	884.7	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB370K5-525AXSP04	-	506.6	382.9	433.7	854.5	-	507	386.1	434.8	844.8	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB370K5-425AXSP04	-	464.6	348.6	396.5	793.2	-	465.3	352.1	397.9	784.7	654	21.3	4"	523	14	4"	785	29.9	4"
EAW-VD15S5ZB550K5-625AXSP04	-	606.7	460.9	520.6	1015.4	-	607.2	464.4	521.9	1003.5	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB550K5-525AXSP04	-	569.4	429.9	487.1	964	-	570	433.7	489.1	954.1	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB550K5-425AXSP02	-	-	-	-	823.1	-	-	-	-	824.9	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB750K5-625AXSP04	-	658.6	499	564.3	1104.4	-	659.6	504.1	566.9	1094.7	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S5ZB750K5-525AXSP04	379.70	617.8	465.8	528.3	1048.8	389.4	619.3	469.8	530.6	1039.2	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB750K5-425AXSP02	-	-	-	-	892.5	-	-	-	-	895.8	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB370C4-625AXSP04	-	561.8	-	482.6	937.5	-	562.2	-	483.2	925.6	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB370C4-525AXSP04	-	528.1	399.2	451.7	891.9	-	528.6	402	453	881.8	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB370C4-425AXSP04	-	482.3	362.5	411.9	824.9	-	483	365.5	413.3	816.9	654	21.3	4"	523	14	4"	785	29.9	4"
EAW-VD15S5ZB550C4-625AXSP04	-	638.5	484.2	548.1	1071.2	-	638.9	488.7	549.4	1058.3	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB550C4-525AXSP04	-	597.3	450.2	511.2	1012.8	376.6	597.9	454.2	512.6	1002.2	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB550C4-425AXSP02	-	-	-	-	859.5	-	-	-	-	861.1	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB750C4-625AXSP04	-	684.8	518.3	586.4	1149.6	-	685.7	523.4	588.9	1138.9	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB750C4-525AXSP04	393.80	640.2	482.7	547.9	1089.8	403.6	642.1	487.2	549.7	1080.1	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB750C4-425AXSP02	-	-	-	-	924.7	-	-	-	-	926.8	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB370C5-625AXSP04	-	561.8	-	482.6	937.5	-	562.2	-	483.2	925.6	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB370C5-525AXSP04	-	528.1	399.2	451.7	891.9	-	528.6	402	453	881.8	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB370C5-425AXSP04	-	482.3	362.5	411.9	824.9	-	483	365.5	413.3	816.9	654	21.3	4"	523	14	4"	785	29.9	4"
EAW-VD15S5ZB550C5-625AXSP04	-	638.5	484.2	548.1	1071.2	-	638.9	488.7	549.4	1058.3	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB550C5-525AXSP04	-	597.3	450.2	511.2	1012.8	376.6	597.9	454.2	512.6	1002.2	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB550C5-425AXSP02	-	-	-	-	859.5	-	-	-	-	861.1	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB750C5-625AXSP04	-	684.8	518.3	586.4	1149.6	-	685.7	523.4	588.9	1138.9	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB750C5-525AXSP04	393.80	640.2	482.7	547.9	1089.8	403.6	642.1	487.2	549.7	1080.1	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB750C5-425AXSP02	-	-	-	-	924.7	-	-	-	-	926.8	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB370K8-625AXSP04	-	538.1	-	462	896.1	-	537.8	-	463	884.7	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB370K8-525AXSP04	-	506.6	382.9	433.7	854.5	-	507	386.1	434.8	844.8	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB370K8-425AXSP04	-	464.6	348.6	396.5	793.2	-	465.3	352.1	397.9	784.7	654	21.3	4"	523	14	4"	785	29.9	4"
EAW-VD15S5ZB550K8-625AXSP04	-	606.7	460.9	520.6	1015.4	-	607.2	464.4	521.9	1003.5	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB550K8-525AXSP04	-	569.4	429.9	487.1	964	-	570	433.7	489.1	954.1	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB550K8-425AXSP02	-	-	-	-	823.1	-	-	-	-	824.9	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S5ZB750K8-625AXSP04	-	658.6	499	564.3	1104.4	-	659.6	504.1	566.9	1094.7	981	20.1	(2) 4"	785	16.1	4"	1177	28.2	(2) 4"
EAW-VD15S5ZB750K8-525AXSP04	379.70	617.8	465.8	528.3	1048.8	389.4	619.3	469.8	530.6	1039.2	812	22.7	4"	649	14.9	4"	974	27.5	(2) 4"
EAW-VD15S5ZB750K8-425AXSP02	-	-	-	-	892.5	-	-	-	-	895.8	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.8	(2) 4"
EAW-VD15S6ZB370K4-625AXSP04	-	657.7	504.2	566.7	1085	-	655.5	505.5	564.9	1070	981	23.6	(2) 4"	785	18.4	4"	1177	33.1	(2) 4"
EAW-VD15S6ZB370K4-525AXSP02	-	-	-	-	975.6	-	-	-	-	971.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB370K4-425AXSP02	-	-	-	-	899.3	-	-	-	-	896.7	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB550K4-625AXSP02	-	-	-	-	1159.3	-	-	-	-	1154.7	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB550K4-525AXSP02	-	-	-	-	1100.2	-	-	-	-	1096.8	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB550K4-425AXSP02	-	-	-	-	1010.2	-	-	-	-	1007.3	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB750K4-625AXSP02	-	-	-	-	1261.2	-	-	-	-	1257.1	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB750K4-525AXSP02	-	-	-	-	1195.6	-	-	-	-	1193.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB750K4-425AXSP02	-	-	-	-	1096.2	-	619.6	-	-	1094.6	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB370K5-625AXSP04	-	657.7	504.2	566.7	1085	-	655.5	505.5	564.9	1070	981	23.6	(2) 4"	785	18.4	4"	1177	33.1	(2) 4"
EAW-VD15S6ZB370K5-525AXSP02	-	-	-	-	975.6	-	-	-	-	971.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB370K5-425AXSP02	-	-	-	-	899.3	-	-	-	-	896.7	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB550K5-625AXSP02	-	-	-	-	1159.3	-	-	-	-	1154.7	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB550K5-525AXSP02	-	-	-	-	1100.2	-	-	-	-	1096.8	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB550K5-425AXSP02	-	-	-	-	1010.2	-	-	-	-	1007.3	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB750K5-625AXSP02	-	-	-	-	1261.2	-	-	-	-	1257.1	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB750K5-525AXSP02	-	-	-	-	1195.6	-	-	-	-	1193.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB750K5-425AXSP02	-	-	-	-	1096.2	-	619.6	-	-	1094.6	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB370C4-625AXSP04	-	687.6	526.6	591.4	1135.2	-	684.5	527.4	590.3	1119.4	981	23.6	(2) 4"	785	18.4	4"	1177	33.1	(2) 4"
EAW-VD15S6ZB370C4-525AXSP02	-	-	-	-	1017.7	-	-	-	-	1014.6	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB370C4-425AXSP02	-	-	-	-	935.8	-	-	-	-	933	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB550C4-625AXSP02	-	-	-	-	1222.3	-	-	-	-	1217.2	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB550C4-525AXSP02	-	-	-	-	1155.1	-	-	-	-	1151.5	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB550C4-425AXSP02	-	-	-	-	1055.3	-	-	-	-	1051.9	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB750C4-625AXSP02	-	-	-	-	1312.2	-	-	-	-	1307.4	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB750C4-525AXSP02	-	-	-	-	1241.5	-	-	-	-	1239.8	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB750C4-425AXSP02	-	626.5	-	-	1134.3	-	641	-	-	1132.7	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB370C5-625AXSP04	-	687.6	526.6	591.4	1135.2	-	684.5	527.4	590.3	1119.4	981	23.6	(2) 4"	785	18.4	4"	1177	33.1	(2) 4"
EAW-VD15S6ZB370C5-525AXSP02	-	-	-	-	1017.7	-	-	-	-	1014.6	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB370C5-425AXSP02	-	-	-	-	935.8	-	-	-	-	933	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB550C5-625AXSP02	-	-	-	-	1222.3	-	-	-	-	1217.2	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB550C5-525AXSP02	-	-	-	-	1155.1	-	-	-	-	1151.5	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB550C5-425AXSP02	-	-	-	-	1055.3	-	-	-	-	1051.9	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB750C5-625AXSP02	-	-	-	-	1312.2	-	-	-	-	1307.4	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB750C5-525AXSP02	-	-	-	-	1241.5	-	-	-	-	1239.8	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB750C5-425AXSP02	-	626.5	-	-	1134.3	-	641	-	-	1132.7	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB370K8-625AXSP04	-	657.7	504.2	566.7	1085	-	655.5	505.5	564.9	1070	981	23.6	(2) 4"	785	18.4	4"	1177	33.1	(2) 4"
EAW-VD15S6ZB370K8-525AXSP02	-	-	-	-	975.6	-	-	-	-	971.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB370K8-425AXSP02	-	-	-	-	899.3	-	-	-	-	896.7	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB550K8-625AXSP02	-	-	-	-	1159.3	-	-	-	-	1154.7	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB550K8-525AXSP02	-	-	-	-	1100.2	-	-	-	-	1096.8	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB550K8-425AXSP02	-	-	-	-	1010.2	-	-	-	-	1007.3	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S6ZB750K8-625AXSP02	-	-	-	-	1261.2	-	-	-	-	1257.1	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD15S6ZB750K8-525AXSP02	-	-	-	-	1195.6	-	-	-	-	1193.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD15S6ZB750K8-425AXSP02	-	-	-	-	1096.2	-	619.6	-	-	1094.6	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD15S1ZK370K4-625AXSP16	-	-	-	-	185.8	-	-	-	-	183.5	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK370K4-525AXSP16	-	103.1	-	-	174.8	-	103.4	-	-	172.9	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK370K4-425AXSP16	-	94.7	-	80.8	162.8	-	95	-	81.3	161.1	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK550K4-625AXSP16	-	125.8	-	-	211.4	-	126.1	-	-	208.9	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK550K4-525AXSP16	-	116.3	-	99.3	197.9	-	116.6	-	99.8	196	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK550K4-425AXSP16	-	106.3	79.5	90.6	183.4	-	106.9	80.4	91.2	181.8	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK750K4-625AXSP16	-	137.2	-	117.4	231	-	137.7	-	118.1	228.5	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK750K4-525AXSP16	-	126.3	94.8	107.9	215.9	-	126.9	96	108.5	214	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK750K4-425AXSP12	-	112.2	-	-	198.8	-	114.1	-	-	197.8	218	20.2	2"	174	13.3	2"	262	22.8	3"
EAW-VD15S1ZK370K5-625AXSP16	-	-	-	-	185.8	-	-	-	-	183.5	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK370K5-525AXSP16	-	103.1	-	-	174.8	-	103.4	-	-	172.9	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK370K5-425AXSP16	-	94.7	-	80.8	162.8	-	95	-	81.3	161.1	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK550K5-625AXSP16	-	125.8	-	-	211.4	-	126.1	-	-	208.9	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK550K5-525AXSP16	-	116.3	-	99.3	197.9	-	116.6	-	99.8	196	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK550K5-425AXSP16	-	106.3	79.5	90.6	183.4	-	106.9	80.4	91.2	181.8	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK750K5-625AXSP16	-	137.2	-	117.4	231	-	137.7	-	118.1	228.5	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK750K5-525AXSP16	-	126.3	94.8	107.9	215.9	-	126.9	96	108.5	214	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK750K5-425AXSP12	-	112.2	-	-	198.8	-	114.1	-	-	197.8	218	20.2	2"	174	13.3	2"	262	22.8	3"
EAW-VD15S1ZK370C4-625AXSP16	-	116.1	-	-	194.5	-	116.4	-	-	192.1	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK370C4-525AXSP16	-	107.5	-	91.8	182.6	-	107.7	-	92.2	180.5	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK370C4-425AXSP16	-	98.4	73.6	83.9	169.2	-	98.8	74.4	84.3	167.4	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK550C4-625AXSP16	-	132.3	-	113.3	222.6	-	132.6	-	113.8	220	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK550C4-525AXSP16	-	121.7	91.3	103.9	207.7	-	122	92.3	104.4	205.5	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK550C4-425AXSP16	-	110.8	82.8	94.5	191.5	-	111.4	83.8	95.1	189.7	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK750C4-625AXSP16	-	142.5	-	121.9	240.5	-	142.9	-	122.7	238	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK750C4-525AXSP16	-	131	98.2	111.9	224.3	-	131.6	99.5	112.5	222	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK750C4-425AXSP12	-	116.2	-	-	205.9	-	117.9	-	-	204.8	218	20.2	2"	174	13.3	2"	262	22.8	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1ZK370C5-625AXSP16	-	116.1	-	-	194.5	-	116.4	-	-	192.1	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK370C5-525AXSP16	-	107.5	-	91.8	182.6	-	107.7	-	92.2	180.5	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK370C5-425AXSP16	-	98.4	73.6	83.9	169.2	-	98.8	74.4	84.3	167.4	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK550C5-625AXSP16	-	132.3	-	113.3	222.6	-	132.6	-	113.8	220	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK550C5-525AXSP16	-	121.7	91.3	103.9	207.7	-	122	92.3	104.4	205.5	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK550C5-425AXSP16	-	110.8	82.8	94.5	191.5	-	111.4	83.8	95.1	189.7	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK750C5-625AXSP16	-	142.5	-	121.9	240.5	-	142.9	-	122.7	238	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK750C5-525AXSP16	-	131	98.2	111.9	224.3	-	131.6	99.5	112.5	222	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK750C5-425AXSP12	-	116.2	-	-	205.9	-	117.9	-	-	204.8	218	20.2	2"	174	13.3	2"	262	22.8	3"
EAW-VD15S1ZK370K8-625AXSP16	-	-	-	-	185.8	-	-	-	-	183.5	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK370K8-525AXSP16	-	103.1	-	-	174.8	-	103.4	-	-	172.9	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK370K8-425AXSP16	-	94.7	-	80.8	162.8	-	95	-	81.3	161.1	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK550K8-625AXSP16	-	125.8	-	-	211.4	-	126.1	-	-	208.9	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK550K8-525AXSP16	-	116.3	-	99.3	197.9	-	116.6	-	99.8	196	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK550K8-425AXSP16	-	106.3	79.5	90.6	183.4	-	106.9	80.4	91.2	181.8	157	23	2"	126	18.3	1-1/2"	189	32.3	2"
EAW-VD15S1ZK750K8-625AXSP16	-	137.2	-	117.4	231	-	137.7	-	118.1	228.5	242	21.6	3"	194	17.4	2"	291	30.3	3"
EAW-VD15S1ZK750K8-525AXSP16	-	126.3	94.8	107.9	215.9	-	126.9	96	108.5	214	194	24.3	2"	155	16	2"	232	34.2	2"
EAW-VD15S1ZK750K8-425AXSP12	-	112.2	-	-	198.8	-	114.1	-	-	197.8	218	20.2	2"	174	13.3	2"	262	22.8	3"
EAW-VD15S2ZK370K4-625AXSP08	-	-	-	-	370.8	-	-	-	-	366.1	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK370K4-525AXSP08	-	208.4	-	-	353	-	208.9	-	-	349.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK370K4-425AXSP08	-	192.5	-	164.2	329.9	-	193.2	-	165.1	326.5	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK550K4-625AXSP08	-	250.6	-	-	421.2	-	251.5	-	-	416.9	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK550K4-525AXSP08	-	234.8	-	200.6	399.8	-	235.8	-	201.9	395.8	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK550K4-425AXSP08	-	216.3	161.5	184.3	372.5	-	217.1	163.6	185.4	369	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK750K4-625AXSP08	-	273.3	-	233.9	460.9	-	274.3	-	235.2	456	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK750K4-525AXSP08	-	255.5	191.8	218.2	436.3	-	256.6	194.2	219.6	432.4	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK750K4-425AXSP08	-	235	175.3	200.1	405.5	-	236.2	177.6	201.6	402.2	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK370K5-625AXSP08	-	-	-	-	370.8	-	-	-	-	366.1	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK370K5-525AXSP08	-	208.4	-	-	353	-	208.9	-	-	349.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK370K5-425AXSP08	-	192.5	-	164.2	329.9	-	193.2	-	165.1	326.5	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK550K5-625AXSP08	-	250.6	-	-	421.2	-	251.5	-	-	416.9	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK550K5-525AXSP08	-	234.8	-	200.6	399.8	-	235.8	-	201.9	395.8	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK550K5-425AXSP08	-	216.3	161.5	184.3	372.5	-	217.1	163.6	185.4	369	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK750K5-625AXSP08	-	273.3	-	233.9	460.9	-	274.3	-	235.2	456	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK750K5-525AXSP08	-	255.5	191.8	218.2	436.3	-	256.6	194.2	219.6	432.4	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK750K5-425AXSP08	-	235	175.3	200.1	405.5	-	236.2	177.6	201.6	402.2	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK370C4-625AXSP08	-	231.7	-	-	388.2	-	231.9	-	-	383.4	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK370C4-525AXSP08	-	217.1	-	185.5	368.3	-	217.6	-	186.6	364.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK370C4-425AXSP08	-	199.8	-	170.3	343.4	-	200.5	151.3	171.2	339.8	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK550C4-625AXSP08	-	263.6	-	225.7	444.2	-	264.2	-	227	438.9	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK550C4-525AXSP08	-	246.1	-	210	419.7	-	246.7	187	211.3	415.2	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK550C4-425AXSP08	-	225.5	168.3	191.9	389	-	226.3	170.5	193.3	385.2	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK750C4-625AXSP08	-	283.9	-	242.8	479.3	-	285.1	-	244.3	475	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK750C4-525AXSP08	-	265	198.7	226.2	453.2	-	266.2	201.2	227.7	449.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK750C4-425AXSP08	-	243.1	181.1	206.8	420.1	-	244.3	183.4	208.3	416.6	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK370C5-625AXSP08	-	231.7	-	-	388.2	-	231.9	-	-	383.4	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK370C5-525AXSP08	-	217.1	-	185.5	368.3	-	217.6	-	186.6	364.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK370C5-425AXSP08	-	199.8	-	170.3	343.4	-	200.5	151.3	171.2	339.8	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK550C5-625AXSP08	-	263.6	-	225.7	444.2	-	264.2	-	227	438.9	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK550C5-525AXSP08	-	246.1	-	210	419.7	-	246.7	187	211.3	415.2	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK550C5-425AXSP08	-	225.5	168.3	191.9	389	-	226.3	170.5	193.3	385.2	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK750C5-625AXSP08	-	283.9	-	242.8	479.3	-	285.1	-	244.3	475	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK750C5-525AXSP08	-	265	198.7	226.2	453.2	-	266.2	201.2	227.7	449.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK750C5-425AXSP08	-	243.1	181.1	206.8	420.1	-	244.3	183.4	208.3	416.6	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK370K8-625AXSP08	-	-	-	-	370.8	-	-	-	-	366.1	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK370K8-525AXSP08	-	208.4	-	-	353	-	208.9	-	-	349.1	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK370K8-425AXSP08	-	192.5	-	164.2	329.9	-	193.2	-	165.1	326.5	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK550K8-625AXSP08	-	250.6	-	-	421.2	-	251.5	-	-	416.9	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK550K8-525AXSP08	-	234.8	-	200.6	399.8	-	235.8	-	201.9	395.8	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK550K8-425AXSP08	-	216.3	161.5	184.3	372.5	-	217.1	163.6	185.4	369	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S2ZK750K8-625AXSP08	-	273.3	-	233.9	460.9	-	274.3	-	235.2	456	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD15S2ZK750K8-525AXSP08	-	255.5	191.8	218.2	436.3	-	256.6	194.2	219.6	432.4	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD15S2ZK750K8-425AXSP08	-	235	175.3	200.1	405.5	-	236.2	177.6	201.6	402.2	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD15S3ZK370K4-625AXSP06	-	337.9	-	-	561.1	-	337.6	-	-	553.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK370K4-525AXSP06	-	319.7	-	273.8	536.6	-	319.5	-	274.4	529.9	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK370K4-425AXSP06	-	292.2	220	249.8	497.5	-	292.3	221.8	250.4	491.6	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK550K4-625AXSP06	-	382.6	-	328.3	637.7	-	382.4	-	329	630.3	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK550K4-525AXSP06	-	360.5	272.7	308.5	607.9	-	360.8	274.5	309.3	601	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK550K4-425AXSP06	-	328.5	246.5	280.6	561	205.7	329.1	248.7	281.2	555.7	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK750K4-625AXSP06	-	416.9	316.6	357.6	697.8	-	417.1	319.4	358.5	689.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK750K4-525AXSP06	-	392.5	296.4	335.8	664.4	-	392.8	298.9	336.7	657.5	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK750K4-425AXSP04	-	332.1	-	-	590.3	-	337.8	-	-	587.4	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S3ZK370K5-625AXSP06	-	337.9	-	-	561.1	-	337.6	-	-	553.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK370K5-525AXSP06	-	319.7	-	273.8	536.6	-	319.5	-	274.4	529.9	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK370K5-425AXSP06	-	292.2	220	249.8	497.5	-	292.3	221.8	250.4	491.6	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK550K5-625AXSP06	-	382.6	-	328.3	637.7	-	382.4	-	329	630.3	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK550K5-525AXSP06	-	360.5	272.7	308.5	607.9	-	360.8	274.5	309.3	601	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK550K5-425AXSP06	-	328.5	246.5	280.6	561	205.7	329.1	248.7	281.2	555.7	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK750K5-625AXSP06	-	416.9	316.6	357.6	697.8	-	417.1	319.4	358.5	689.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK750K5-525AXSP06	-	392.5	296.4	335.8	664.4	-	392.8	298.9	336.7	657.5	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK750K5-425AXSP04	-	332.1	-	-	590.3	-	337.8	-	-	587.4	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S3ZK370C4-625AXSP06	-	353.1	-	303.3	586.9	-	352.9	-	303.6	579.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK370C4-525AXSP06	-	333.2	252.3	285.5	560.5	-	332.9	253.9	285.8	553.4	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK370C4-425AXSP06	-	303.4	228.4	259.1	517.2	-	303.8	229.9	260.1	511.7	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK550C4-625AXSP06	-	402.6	305.6	345.6	672.4	-	402.3	307.9	345.9	663.7	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK550C4-525AXSP06	-	377.5	285.4	323.1	638.2	-	377.6	287.3	323.9	630.5	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK550C4-425AXSP04	-	319	-	-	565.6	-	323.8	-	-	562	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S3ZK750C4-625AXSP06	-	433.2	329	371.9	725.8	-	433.6	331.7	372.9	718.2	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK750C4-525AXSP06	-	406.8	307.2	348.2	689.4	257	407.7	309.9	349.1	682.2	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK750C4-425AXSP04	-	343.9	-	-	610.4	-	349.2	-	-	607.4	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S3ZK370C5-625AXSP06	-	353.1	-	303.3	586.9	-	352.9	-	303.6	579.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK370C5-525AXSP06	-	333.2	252.3	285.5	560.5	-	332.9	253.9	285.8	553.4	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK370C5-425AXSP06	-	303.4	228.4	259.1	517.2	-	303.8	229.9	260.1	511.7	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK550C5-625AXSP06	-	402.6	305.6	345.6	672.4	-	402.3	307.9	345.9	663.7	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK550C5-525AXSP06	-	377.5	285.4	323.1	638.2	-	377.6	287.3	323.9	630.5	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK550C5-425AXSP04	-	319	-	-	565.6	-	323.8	-	-	562	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S3ZK750C5-625AXSP06	-	433.2	329	371.9	725.8	-	433.6	331.7	372.9	718.2	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK750C5-525AXSP06	-	406.8	307.2	348.2	689.4	257	407.7	309.9	349.1	682.2	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK750C5-425AXSP04	-	343.9	-	-	610.4	-	349.2	-	-	607.4	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S3ZK370K8-625AXSP06	-	337.9	-	-	561.1	-	337.6	-	-	553.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK370K8-525AXSP06	-	319.7	-	273.8	536.6	-	319.5	-	274.4	529.9	545	21.1	4"	436	16.4	3"	654	29.6	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3ZK370K8-425AXSP06	-	292.2	220	249.8	497.5	-	292.3	221.8	250.4	491.6	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK550K8-625AXSP06	-	382.6	-	328.3	637.7	-	382.4	-	329	630.3	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK550K8-525AXSP06	-	360.5	272.7	308.5	607.9	-	360.8	274.5	309.3	601	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK550K8-425AXSP06	-	328.5	246.5	280.6	561	205.7	329.1	248.7	281.2	555.7	436	22.9	3"	349	15.1	3"	523	28.7	4"
EAW-VD15S3ZK750K8-625AXSP06	-	416.9	316.6	357.6	697.8	-	417.1	319.4	358.5	689.5	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD15S3ZK750K8-525AXSP06	-	392.5	296.4	335.8	664.4	-	392.8	298.9	336.7	657.5	545	21.1	4"	436	16.4	3"	654	29.6	4"
EAW-VD15S3ZK750K8-425AXSP04	-	332.1	-	-	590.3	-	337.8	-	-	587.4	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD15S4ZK370K4-625AXSP04	-	-	-	-	740.7	-	-	-	-	731.5	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK370K4-525AXSP04	-	416.2	-	-	706.1	-	417.8	-	-	698.3	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK370K4-425AXSP04	-	381.6	-	325.3	655.4	-	383	-	327.2	648.7	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK550K4-625AXSP04	-	500.6	-	-	841.5	-	501.8	-	-	832.8	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK550K4-525AXSP04	-	469.6	-	400.6	799.6	-	470.9	-	403.1	791.6	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK550K4-425AXSP04	-	428.6	319.6	364.9	738.8	-	430.9	324.4	367.8	732.1	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK750K4-625AXSP04	-	545.2	-	466.5	920.7	-	547.2	-	469.8	911	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK750K4-525AXSP04	-	511	382.9	435.7	872.6	-	513.1	388.4	439.2	864.8	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK750K4-425AXSP04	-	465.4	346.9	396	805.3	-	468	352.1	399.2	798.9	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK370K5-625AXSP04	-	-	-	-	740.7	-	-	-	-	731.5	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK370K5-525AXSP04	-	416.2	-	-	706.1	-	417.8	-	-	698.3	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK370K5-425AXSP04	-	381.6	-	325.3	655.4	-	383	-	327.2	648.7	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK550K5-625AXSP04	-	500.6	-	-	841.5	-	501.8	-	-	832.8	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK550K5-525AXSP04	-	469.6	-	400.6	799.6	-	470.9	-	403.1	791.6	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK550K5-425AXSP04	-	428.6	319.6	364.9	738.8	-	430.9	324.4	367.8	732.1	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK750K5-625AXSP04	-	545.2	-	466.5	920.7	-	547.2	-	469.8	911	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK750K5-525AXSP04	-	511	382.9	435.7	872.6	-	513.1	388.4	439.2	864.8	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK750K5-425AXSP04	-	465.4	346.9	396	805.3	-	468	352.1	399.2	798.9	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK370C4-625AXSP04	-	462.2	-	-	775.5	-	463.2	-	-	765.9	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK370C4-525AXSP04	-	433.6	-	-	736.6	-	435.2	-	-	728.2	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK370C4-425AXSP04	-	396	-	337.8	681.3	-	397.5	-	339.8	674.2	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK550C4-625AXSP04	-	526.6	-	-	887.3	-	527.8	-	-	876.9	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK550C4-525AXSP04	-	491.5	-	420.1	839.3	-	493.3	-	422	830.4	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK550C4-425AXSP04	-	446.7	333	380.5	771.5	-	449.1	337.4	382.8	764.1	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK750C4-625AXSP04	-	566.4	-	485	957.5	-	568.8	-	488	948.8	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK750C4-525AXSP04	-	529.3	396.7	451.7	906.4	-	532.4	402.4	455.3	898.2	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK750C4-425AXSP04	-	481.4	358.8	409.2	833.1	-	484	363.6	412.4	826.2	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK370C5-625AXSP04	-	462.2	-	-	775.5	-	463.2	-	-	765.9	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK370C5-525AXSP04	-	433.6	-	-	736.6	-	435.2	-	-	728.2	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK370C5-425AXSP04	-	396	-	337.8	681.3	-	397.5	-	339.8	674.2	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK550C5-625AXSP04	-	526.6	-	-	887.3	-	527.8	-	-	876.9	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK550C5-525AXSP04	-	491.5	-	420.1	839.3	-	493.3	-	422	830.4	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK550C5-425AXSP04	-	446.7	333	380.5	771.5	-	449.1	337.4	382.8	764.1	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK750C5-625AXSP04	-	566.4	-	485	957.5	-	568.8	-	488	948.8	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK750C5-525AXSP04	-	529.3	396.7	451.7	906.4	-	532.4	402.4	455.3	898.2	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK750C5-425AXSP04	-	481.4	358.8	409.2	833.1	-	484	363.6	412.4	826.2	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK370K8-625AXSP04	-	-	-	-	740.7	-	-	-	-	731.5	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK370K8-525AXSP04	-	416.2	-	-	706.1	-	417.8	-	-	698.3	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK370K8-425AXSP04	-	381.6	-	325.3	655.4	-	383	-	327.2	648.7	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK550K8-625AXSP04	-	500.6	-	-	841.5	-	501.8	-	-	832.8	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK550K8-525AXSP04	-	469.6	-	400.6	799.6	-	470.9	-	403.1	791.6	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK550K8-425AXSP04	-	428.6	319.6	364.9	738.8	-	430.9	324.4	367.8	732.1	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S4ZK750K8-625AXSP04	-	545.2	-	466.5	920.7	-	547.2	-	469.8	911	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD15S4ZK750K8-525AXSP04	-	511	382.9	435.7	872.6	-	513.1	388.4	439.2	864.8	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD15S4ZK750K8-425AXSP04	-	465.4	346.9	396	805.3	-	468	352.1	399.2	798.9	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD15S5ZK370K4-625AXSP04	-	567.2	-	488.4	937.3	-	565.4	-	487.5	923.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK370K4-525AXSP04	-	534.2	406.3	458.8	893.2	-	533.1	408.3	458	881.1	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK370K4-425AXSP02	-	-	-	-	773.5	-	-	-	-	771.6	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550K4-625AXSP04	-	641.7	490.1	552.2	1065.2	-	640.4	492.3	551.2	1050.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK550K4-525AXSP04	376.60	602.5	457.2	516.4	1011.9	383.8	601.4	459.6	517	999.2	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK550K4-425AXSP02	-	-	-	-	871.2	-	-	-	-	870.3	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750K4-625AXSP04	-	700.1	533.6	600.9	1164.4	-	698.7	536	601.4	1150.6	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK750K4-525AXSP02	-	-	-	-	1035.3	-	-	-	-	1033.6	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK750K4-425AXSP02	-	-	-	-	948	-	-	-	-	948.4	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370K5-625AXSP04	-	567.2	-	488.4	937.3	-	565.4	-	487.5	923.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK370K5-525AXSP04	-	534.2	406.3	458.8	893.2	-	533.1	408.3	458	881.1	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK370K5-425AXSP02	-	-	-	-	773.5	-	-	-	-	771.6	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550K5-625AXSP04	-	641.7	490.1	552.2	1065.2	-	640.4	492.3	551.2	1050.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK550K5-525AXSP04	376.60	602.5	457.2	516.4	1011.9	383.8	601.4	459.6	517	999.2	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK550K5-425AXSP02	-	-	-	-	871.2	-	-	-	-	870.3	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750K5-625AXSP04	-	700.1	533.6	600.9	1164.4	-	698.7	536	601.4	1150.6	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK750K5-525AXSP02	-	-	-	-	1035.3	-	-	-	-	1033.6	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK750K5-425AXSP02	-	-	-	-	948	-	-	-	-	948.4	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370C4-625AXSP04	-	592.8	-	510.1	980.3	-	591	454.6	509.3	966.9	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK370C4-525AXSP04	-	556.8	423.5	477.9	933.1	-	555.5	425	477.6	920.1	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK370C4-425AXSP02	-	-	-	-	804.7	-	-	-	-	802.6	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550C4-625AXSP04	-	675.2	515	580.6	1122	-	673.8	517.4	579.5	1107.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK550C4-525AXSP02	-	-	-	-	996.4	-	-	-	-	993.1	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK550C4-425AXSP02	-	-	-	-	908.9	-	-	-	-	907.8	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750C4-625AXSP04	458.50	727.5	553.9	624.9	1212.5	466.6	726.4	556.7	624.9	1198.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK750C4-525AXSP02	-	-	-	-	1074.8	-	-	-	-	1073.1	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK750C4-425AXSP02	-	-	-	-	981.4	-	-	-	-	980.2	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370C5-625AXSP04	-	592.8	-	510.1	980.3	-	591	454.6	509.3	966.9	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK370C5-525AXSP04	-	556.8	423.5	477.9	933.1	-	555.5	425	477.6	920.1	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK370C5-425AXSP02	-	-	-	-	804.7	-	-	-	-	802.6	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550C5-625AXSP04	-	675.2	515	580.6	1122	-	673.8	517.4	579.5	1107.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK550C5-525AXSP02	-	-	-	-	996.4	-	-	-	-	993.1	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK550C5-425AXSP02	-	-	-	-	908.9	-	-	-	-	907.8	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750C5-625AXSP04	458.50	727.5	553.9	624.9	1212.5	466.6	726.4	556.7	624.9	1198.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK750C5-525AXSP02	-	-	-	-	1074.8	-	-	-	-	1073.1	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK750C5-425AXSP02	-	-	-	-	981.4	-	-	-	-	980.2	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370K8-625AXSP04	-	567.2	-	488.4	937.3	-	565.4	-	487.5	923.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK370K8-525AXSP04	-	534.2	406.3	458.8	893.2	-	533.1	408.3	458	881.1	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK370K8-425AXSP02	-	-	-	-	773.5	-	-	-	-	771.6	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550K8-625AXSP04	-	641.7	490.1	552.2	1065.2	-	640.4	492.3	551.2	1050.4	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK550K8-525AXSP04	376.60	602.5	457.2	516.4	1011.9	383.8	601.4	459.6	517	999.2	812	24.6	4"	649	16.2	4"	974	30.2	(2) 4"
EAW-VD15S5ZK550K8-425AXSP02	-	-	-	-	871.2	-	-	-	-	870.3	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750K8-625AXSP04	-	700.1	533.6	600.9	1164.4	-	698.7	536	601.4	1150.6	981	22	(2) 4"	785	17.4	4"	1177	30.9	(2) 4"
EAW-VD15S5ZK750K8-525AXSP02	-	-	-	-	1035.3	-	-	-	-	1033.6	1635	14.4	(2) 4"	1308	9.4	(2) 4"	1962	17	(3) 4"
EAW-VD15S5ZK750K8-425AXSP02	-	-	-	-	948	-	-	-	-	948.4	1308	12.9	(2) 4"	1046	8.5	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S6ZK370K4-625AXSP04	-	692.2	533.2	597.2	1132.2	-	687.3	532.5	593.7	1115.4	981	25.9	(2) 4"	785	20	4"	1177	36.3	(2) 4"
EAW-VD15S6ZK370K4-525AXSP02	-	-	-	-	1026	-	-	-	-	1018.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK370K4-425AXSP02	-	-	-	-	946.5	-	-	-	-	941.2	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK550K4-625AXSP02	-	-	-	-	1223.1	-	-	-	-	1213.8	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6ZK550K4-525AXSP02	-	-	-	-	1160.7	-	-	-	-	1154.1	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK550K4-425AXSP02	-	-	-	-	1066.8	-	610.1	-	-	1060.8	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK750K4-625AXSP02	-	-	-	-	1335.8	-	-	-	-	1328.6	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK750K4-525AXSP02	-	-	-	-	1265.6	-	-	-	-	1259.8	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK750K4-425AXSP02	-	650.6	-	-	1159.9	-	662.3	-	-	1156.5	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK370K5-625AXSP04	-	692.2	533.2	597.2	1132.2	-	687.3	532.5	593.7	1115.4	981	25.9	(2) 4"	785	20	4"	1177	36.3	(2) 4"
EAW-VD15S6ZK370K5-525AXSP02	-	-	-	-	1026	-	-	-	-	1018.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK370K5-425AXSP02	-	-	-	-	946.5	-	-	-	-	941.2	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK550K5-625AXSP02	-	-	-	-	1223.1	-	-	-	-	1213.8	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK550K5-525AXSP02	-	-	-	-	1160.7	-	-	-	-	1154.1	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK550K5-425AXSP02	-	-	-	-	1066.8	-	610.1	-	-	1060.8	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK750K5-625AXSP02	-	-	-	-	1335.8	-	-	-	-	1328.6	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK750K5-525AXSP02	-	-	-	-	1265.6	-	-	-	-	1259.8	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK750K5-425AXSP02	-	650.6	-	-	1159.9	-	662.3	-	-	1156.5	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK370C4-625AXSP02	-	-	-	-	1126.5	-	-	-	-	1118.1	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK370C4-525AXSP02	-	-	-	-	1071.3	-	-	-	-	1063.6	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK370C4-425AXSP02	-	-	-	-	983.5	-	-	-	-	977.8	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK550C4-625AXSP02	-	-	-	-	1287.7	-	-	-	-	1279.2	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK550C4-525AXSP02	-	-	-	-	1217.8	-	-	-	-	1210.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK550C4-425AXSP02	-	625.2	-	-	1113.4	-	635.2	-	-	1106.7	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK750C4-625AXSP02	-	-	-	-	1388.8	-	-	-	-	1381.8	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK750C4-525AXSP02	-	-	-	-	1314.2	-	758.2	-	-	1308.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK750C4-425AXSP02	-	673.5	-	-	1201.1	-	684.5	-	-	1195.5	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK370C5-625AXSP02	-	-	-	-	1126.5	-	-	-	-	1118.1	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK370C5-525AXSP02	-	-	-	-	1071.3	-	-	-	-	1063.6	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK370C5-425AXSP02	-	-	-	-	983.5	-	-	-	-	977.8	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK550C5-625AXSP02	-	-	-	-	1287.7	-	-	-	-	1279.2	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK550C5-525AXSP02	-	-	-	-	1217.8	-	-	-	-	1210.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK550C5-425AXSP02	-	625.2	-	-	1113.4	-	635.2	-	-	1106.7	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK750C5-625AXSP02	-	-	-	-	1388.8	-	-	-	-	1381.8	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK750C5-525AXSP02	-	-	-	-	1314.2	-	758.2	-	-	1308.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK750C5-425AXSP02	-	673.5	-	-	1201.1	-	684.5	-	-	1195.5	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK370K8-625AXSP04	-	692.2	533.2	597.2	1132.2	-	687.3	532.5	593.7	1115.4	981	25.9	(2) 4"	785	20	4"	1177	36.3	(2) 4"
EAW-VD15S6ZK370K8-525AXSP02	-	-	-	-	1026	-	-	-	-	1018.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK370K8-425AXSP02	-	-	-	-	946.5	-	-	-	-	941.2	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK550K8-625AXSP02	-	-	-	-	1223.1	-	-	-	-	1213.8	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK550K8-525AXSP02	-	-	-	-	1160.7	-	-	-	-	1154.1	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK550K8-425AXSP02	-	-	-	-	1066.8	-	610.1	-	-	1060.8	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S6ZK750K8-625AXSP02	-	-	-	-	1335.8	-	-	-	-	1328.6	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD15S6ZK750K8-525AXSP02	-	-	-	-	1265.6	-	-	-	-	1259.8	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD15S6ZK750K8-425AXSP02	-	650.6	-	-	1159.9	-	662.3	-	-	1156.5	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD15S1PB370K4-625AXSP16	-	91.8	-	-	155.9	-	92.5	-	-	154.7	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB370K4-525AXSP16	-	85.3	-	72.6	146.8	-	86	-	73.4	145.8	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB370K4-425AXSP16	-	79.6	59.1	67.6	138.7	-	80.5	60.3	68.5	137.9	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB550K4-625AXSP16	-	102.4	-	87.4	174.7	-	103.4	-	88.4	173.5	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB550K4-525AXSP16	-	94.8	70.6	80.6	163.9	-	95.8	71.9	81.7	163.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB550K4-425AXSP16	-	88.4	65.4	75.1	154.5	-	89.4	66.8	76.1	153.7	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB750K4-625AXSP16	-	109.8	-	93.7	187.7	-	111.1	-	95.1	187.1	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB750K4-525AXSP16	-	101.7	75.6	86.4	176.1	-	102.8	77.2	87.6	175.5	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB750K4-425AXSP12	-	88.2	-	74.2	159.3	-	90.3	-	76.2	159.3	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S1PB370K5-625AXSP16	-	91.8	-	-	155.9	-	92.5	-	-	154.7	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB370K5-525AXSP16	-	85.3	-	72.6	146.8	-	86	-	73.4	145.8	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB370K5-425AXSP16	-	79.6	59.1	67.6	138.7	-	80.5	60.3	68.5	137.9	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB550K5-625AXSP16	-	102.4	-	87.4	174.7	-	103.4	-	88.4	173.5	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB550K5-525AXSP16	-	94.8	70.6	80.6	163.9	-	95.8	71.9	81.7	163.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB550K5-425AXSP16	-	88.4	65.4	75.1	154.5	-	89.4	66.8	76.1	153.7	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB750K5-625AXSP16	-	109.8	-	93.7	187.7	-	111.1	-	95.1	187.1	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB750K5-525AXSP16	-	101.7	75.6	86.4	176.1	-	102.8	77.2	87.6	175.5	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB750K5-425AXSP12	-	88.2	-	74.2	159.3	-	90.3	-	76.2	159.3	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S1PB370C4-625AXSP16	-	95.6	-	-	162.4	-	96.4	-	-	161.3	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB370C4-525AXSP16	-	88.6	-	75.5	153	-	89.6	67.4	76.4	152.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB370C4-425AXSP16	-	82.7	61.3	70.3	144.3	-	83.6	62.6	71.2	143.5	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB550C4-625AXSP16	-	107.9	-	92.1	184.3	-	109	-	93.2	183.3	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB550C4-525AXSP16	-	99.7	74	84.8	172.5	-	100.6	75.6	85.8	171.7	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB550C4-425AXSP12	-	86.1	-	-	155.4	-	88.1	-	74.4	155.3	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S1PB750C4-625AXSP16	-	113.7	85	97	194.8	-	115.1	86.9	98.4	194	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB750C4-525AXSP16	-	105.2	78.2	89.5	182.6	-	106.5	79.8	90.7	182.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB750C4-425AXSP12	-	91.3	-	76.7	164.8	-	93.4	-	78.8	165.1	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S1PB370C5-625AXSP16	-	95.6	-	-	162.4	-	96.4	-	-	161.3	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB370C5-525AXSP16	-	88.6	-	75.5	153	-	89.6	67.4	76.4	152.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB370C5-425AXSP16	-	82.7	61.3	70.3	144.3	-	83.6	62.6	71.2	143.5	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB550C5-625AXSP16	-	107.9	-	92.1	184.3	-	109	-	93.2	183.3	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB550C5-525AXSP16	-	99.7	74	84.8	172.5	-	100.6	75.6	85.8	171.7	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB550C5-425AXSP12	-	86.1	-	-	155.4	-	88.1	-	74.4	155.3	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S1PB750C5-625AXSP16	-	113.7	85	97	194.8	-	115.1	86.9	98.4	194	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB750C5-525AXSP16	-	105.2	78.2	89.5	182.6	-	106.5	79.8	90.7	182.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB750C5-425AXSP12	-	91.3	-	76.7	164.8	-	93.4	-	78.8	165.1	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S1PB370K8-625AXSP16	-	91.8	-	-	155.9	-	92.5	-	-	154.7	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB370K8-525AXSP16	-	85.3	-	72.6	146.8	-	86	-	73.4	145.8	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB370K8-425AXSP16	-	79.6	59.1	67.6	138.7	-	80.5	60.3	68.5	137.9	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB550K8-625AXSP16	-	102.4	-	87.4	174.7	-	103.4	-	88.4	173.5	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB550K8-525AXSP16	-	94.8	70.6	80.6	163.9	-	95.8	71.9	81.7	163.1	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB550K8-425AXSP16	-	88.4	65.4	75.1	154.5	-	89.4	66.8	76.1	153.7	121	23	1-1/2"	97	15.1	1-1/2"	145	28.6	2"
EAW-VD15S1PB750K8-625AXSP16	-	109.8	-	93.7	187.7	-	111.1	-	95.1	187.1	182	22.1	2"	145	14.6	2"	218	31.1	2"
EAW-VD15S1PB750K8-525AXSP16	-	101.7	75.6	86.4	176.1	-	102.8	77.2	87.6	175.5	145	21	2"	116	16.3	1-1/2"	174	29.5	2"
EAW-VD15S1PB750K8-425AXSP12	-	88.2	-	74.2	159.3	-	90.3	-	76.2	159.3	157	16.6	2"	126	13.8	1-1/2"	189	23.3	2"
EAW-VD15S2PB370K4-625AXSP08	-	183	-	-	310.8	-	184.6	-	-	308.6	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB370K4-525AXSP08	-	173.3	-	147.4	297.7	-	174.7	-	149.2	296.2	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB370K4-425AXSP08	-	158.4	117.5	134.6	276.2	-	160.2	119.9	136.3	274.6	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB550K4-625AXSP08	-	204	-	174.1	348	-	205.9	-	176.1	346.1	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB550K4-525AXSP08	-	192.7	143.5	164	332.6	-	194.7	146.4	166.1	330.9	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB550K4-425AXSP08	-	176	130.1	149.3	307.7	-	177.8	132.8	151.3	306.4	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB750K4-625AXSP08	-	218.7	-	186.6	374.5	-	221.4	-	189.3	372.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB750K4-525AXSP08	-	206.8	153.8	176	358.1	-	209	157.2	178.4	356.7	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB750K4-425AXSP08	-	188.7	139.5	160.1	330.9	115.6	190.8	142.5	162.3	329.6	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB370K5-625AXSP08	-	183	-	-	310.8	-	184.6	-	-	308.6	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB370K5-525AXSP08	-	173.3	-	147.4	297.7	-	174.7	-	149.2	296.2	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB370K5-425AXSP08	-	158.4	117.5	134.6	276.2	-	160.2	119.9	136.3	274.6	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB550K5-625AXSP08	-	204	-	174.1	348	-	205.9	-	176.1	346.1	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB550K5-525AXSP08	-	192.7	143.5	164	332.6	-	194.7	146.4	166.1	330.9	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB550K5-425AXSP08	-	176	130.1	149.3	307.7	-	177.8	132.8	151.3	306.4	242	17.5	3"	194	14.5	2"	291	24.5	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S2PB750K5-625AXSP08	-	218.7	-	186.6	374.5	-	221.4	-	189.3	372.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB750K5-525AXSP08	-	206.8	153.8	176	358.1	-	209	157.2	178.4	356.7	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB750K5-425AXSP08	-	188.7	139.5	160.1	330.9	115.6	190.8	142.5	162.3	329.6	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB370C4-625AXSP08	-	190.4	-	-	323.7	-	192.1	-	-	321.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB370C4-525AXSP08	-	180.4	-	153.6	310.4	-	182	-	155.3	308.5	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB370C4-425AXSP08	-	164.7	122	139.8	287.4	-	166.4	124.5	141.6	285.9	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB550C4-625AXSP08	-	214.8	-	183.4	367.7	-	217.1	-	185.7	365.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB550C4-525AXSP08	-	202.7	150.9	172.4	350.7	-	204.9	153.7	174.7	348.9	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB550C4-425AXSP08	-	184.2	136.3	156.4	322.6	112.9	186.2	139	158.5	321.2	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB750C4-625AXSP08	-	226.4	169.3	193.3	388.2	-	229.3	173	196	387.1	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB750C4-525AXSP08	-	214.1	159.2	182.1	371.4	-	216.6	162.6	184.7	370.2	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB750C4-425AXSP08	114.60	195.2	144.3	165.7	342.4	119.5	197.4	147.4	168	341.7	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB370C5-625AXSP08	-	190.4	-	-	323.7	-	192.1	-	-	321.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB370C5-525AXSP08	-	180.4	-	153.6	310.4	-	182	-	155.3	308.5	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB370C5-425AXSP08	-	164.7	122	139.8	287.4	-	166.4	124.5	141.6	285.9	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB550C5-625AXSP08	-	214.8	-	183.4	367.7	-	217.1	-	185.7	365.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB550C5-525AXSP08	-	202.7	150.9	172.4	350.7	-	204.9	153.7	174.7	348.9	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB550C5-425AXSP08	-	184.2	136.3	156.4	322.6	112.9	186.2	139	158.5	321.2	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB750C5-625AXSP08	-	226.4	169.3	193.3	388.2	-	229.3	173	196	387.1	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB750C5-525AXSP08	-	214.1	159.2	182.1	371.4	-	216.6	162.6	184.7	370.2	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB750C5-425AXSP08	114.60	195.2	144.3	165.7	342.4	119.5	197.4	147.4	168	341.7	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB370K8-625AXSP08	-	183	-	-	310.8	-	184.6	-	-	308.6	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB370K8-525AXSP08	-	173.3	-	147.4	297.7	-	174.7	-	149.2	296.2	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB370K8-425AXSP08	-	158.4	117.5	134.6	276.2	-	160.2	119.9	136.3	274.6	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB550K8-625AXSP08	-	204	-	174.1	348	-	205.9	-	176.1	346.1	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB550K8-525AXSP08	-	192.7	143.5	164	332.6	-	194.7	146.4	166.1	330.9	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB550K8-425AXSP08	-	176	130.1	149.3	307.7	-	177.8	132.8	151.3	306.4	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S2PB750K8-625AXSP08	-	218.7	-	186.6	374.5	-	221.4	-	189.3	372.8	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD15S2PB750K8-525AXSP08	-	206.8	153.8	176	358.1	-	209	157.2	178.4	356.7	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD15S2PB750K8-425AXSP08	-	188.7	139.5	160.1	330.9	115.6	190.8	142.5	162.3	329.6	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD15S3PB370K4-625AXSP06	-	278.4	-	238.3	468.9	-	279.8	-	239.9	465.1	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB370K4-525AXSP06	-	262.1	196.7	223.9	447.7	-	263.9	199.7	225.8	444.2	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB370K4-425AXSP06	-	237.6	177.3	202.2	411.4	147.4	239.5	179.8	204	408.5	315	19.3	3"	252	12.8	3"	378	27.1	3"
EAW-VD15S3PB550K4-625AXSP06	-	310.1	233.9	265.3	525.2	-	312.2	237.3	267.5	521.6	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB550K4-525AXSP06	-	291.6	218.6	248.8	499.5	-	293.7	221.7	251.1	496.9	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB550K4-425AXSP04	-	246.7	-	-	445.7	-	253	-	-	445.5	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB750K4-625AXSP06	-	333	250.6	284.4	565.1	-	335.6	254.9	287.6	561.9	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB750K4-525AXSP06	189.50	313.1	234.4	266.7	537.8	195.7	315.4	238.1	269.7	535.1	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB750K4-425AXSP04	-	265	-	-	478.8	-	271.4	-	229.1	479.4	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB370K5-625AXSP06	-	278.4	-	238.3	468.9	-	279.8	-	239.9	465.1	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB370K5-525AXSP06	-	262.1	196.7	223.9	447.7	-	263.9	199.7	225.8	444.2	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB370K5-425AXSP06	-	237.6	177.3	202.2	411.4	147.4	239.5	179.8	204	408.5	315	19.3	3"	252	12.8	3"	378	27.1	3"
EAW-VD15S3PB550K5-625AXSP06	-	310.1	233.9	265.3	525.2	-	312.2	237.3	267.5	521.6	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB550K5-525AXSP06	-	291.6	218.6	248.8	499.5	-	293.7	221.7	251.1	496.9	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB550K5-425AXSP04	-	246.7	-	-	445.7	-	253	-	-	445.5	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB750K5-625AXSP06	-	333	250.6	284.4	565.1	-	335.6	254.9	287.6	561.9	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB750K5-525AXSP06	189.50	313.1	234.4	266.7	537.8	195.7	315.4	238.1	269.7	535.1	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB750K5-425AXSP04	-	265	-	-	478.8	-	271.4	-	229.1	479.4	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB370C4-625AXSP06	-	289.3	-	247.8	488.4	-	291.1	-	249.8	485	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB370C4-525AXSP06	-	272.9	204.8	232.9	466.2	-	274.5	207.7	234.7	463.3	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB370C4-425AXSP06	148.10	247	184	210.1	427.9	152.9	248.8	186.8	212.1	425.1	315	19.3	3"	252	12.8	3"	378	27.1	3"
EAW-VD15S3PB550C4-625AXSP06	-	327.2	246.3	279.5	554.2	-	329.1	250	282.1	550.7	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB550C4-525AXSP06	185.70	306.9	229.5	261.5	526.7	191.8	308.7	233.3	264.1	523.3	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB550C4-425AXSP04	-	258.4	-	-	467.6	-	264.6	-	-	467.4	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB750C4-625AXSP06	-	344.8	259.1	294.8	585.9	-	347.7	263.8	297.8	582.8	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB750C4-525AXSP06	196.00	324.2	242.2	276.3	557.8	202.7	326.9	246.4	279.2	555.4	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB750C4-425AXSP04	-	273.8	-	230.2	496	-	280.6	-	237	496.8	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB370C5-625AXSP06	-	289.3	-	247.8	488.4	-	291.1	-	249.8	485	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB370C5-525AXSP06	-	272.9	204.8	232.9	466.2	-	274.5	207.7	234.7	463.3	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB370C5-425AXSP06	148.10	247	184	210.1	427.9	152.9	248.8	186.8	212.1	425.1	315	19.3	3"	252	12.8	3"	378	27.1	3"
EAW-VD15S3PB550C5-625AXSP06	-	327.2	246.3	279.5	554.2	-	329.1	250	282.1	550.7	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB550C5-525AXSP06	185.70	306.9	229.5	261.5	526.7	191.8	308.7	233.3	264.1	523.3	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB550C5-425AXSP04	-	258.4	-	-	467.6	-	264.6	-	-	467.4	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB750C5-625AXSP06	-	344.8	259.1	294.8	585.9	-	347.7	263.8	297.8	582.8	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB750C5-525AXSP06	196.00	324.2	242.2	276.3	557.8	202.7	326.9	246.4	279.2	555.4	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB750C5-425AXSP04	-	273.8	-	230.2	496	-	280.6	-	237	496.8	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB370K8-625AXSP06	-	278.4	-	238.3	468.9	-	279.8	-	239.9	465.1	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB370K8-525AXSP06	-	262.1	196.7	223.9	447.7	-	263.9	199.7	225.8	444.2	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB370K8-425AXSP06	-	237.6	177.3	202.2	411.4	147.4	239.5	179.8	204	408.5	315	19.3	3"	252	12.8	3"	378	27.1	3"
EAW-VD15S3PB550K8-625AXSP06	-	310.1	233.9	265.3	525.2	-	312.2	237.3	267.5	521.6	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB550K8-525AXSP06	-	291.6	218.6	248.8	499.5	-	293.7	221.7	251.1	496.9	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB550K8-425AXSP04	-	246.7	-	-	445.7	-	253	-	-	445.5	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S3PB750K8-625AXSP06	-	333	250.6	284.4	565.1	-	335.6	254.9	287.6	561.9	484	21.8	3"	388	14.4	3"	581	26.5	4"
EAW-VD15S3PB750K8-525AXSP06	189.50	313.1	234.4	266.7	537.8	195.7	315.4	238.1	269.7	535.1	400	20.5	3"	320	13.5	3"	480	28.7	3"
EAW-VD15S3PB750K8-425AXSP04	-	265	-	-	478.8	-	271.4	-	229.1	479.4	484	16	3"	388	10.5	3"	581	18.3	4"
EAW-VD15S4PB370K4-625AXSP04	-	363.1	-	-	617.9	-	366.4	-	-	613.7	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB370K4-525AXSP04	-	343.5	-	292.6	591.7	-	347	-	296.2	587.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB370K4-425AXSP04	-	314.1	232.4	266.8	547.7	-	317.3	237.2	270.2	545.4	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB550K4-625AXSP04	-	404.6	-	345.1	691.9	-	408.6	-	349.8	688.1	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB550K4-525AXSP04	-	381.9	284.2	324.9	660.7	-	386	289.9	329.2	657.4	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB550K4-425AXSP04	-	348.3	257.6	295.4	609.9	-	352.1	263.2	299.4	607.5	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB750K4-625AXSP04	-	433.7	-	369.9	744.3	-	439.2	-	375.4	741.1	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB750K4-525AXSP04	-	409.8	304.4	348.6	711.3	-	415	311.2	353.3	708.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB750K4-425AXSP04	-	373.4	275.7	316.5	655.7	228.6	378.3	281.7	321.5	654.1	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB370K5-625AXSP04	-	363.1	-	-	617.9	-	366.4	-	-	613.7	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB370K5-525AXSP04	-	343.5	-	292.6	591.7	-	347	-	296.2	587.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB370K5-425AXSP04	-	314.1	232.4	266.8	547.7	-	317.3	237.2	270.2	545.4	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB550K5-625AXSP04	-	404.6	-	345.1	691.9	-	408.6	-	349.8	688.1	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB550K5-525AXSP04	-	381.9	284.2	324.9	660.7	-	386	289.9	329.2	657.4	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB550K5-425AXSP04	-	348.3	257.6	295.4	609.9	-	352.1	263.2	299.4	607.5	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB750K5-625AXSP04	-	433.7	-	369.9	744.3	-	439.2	-	375.4	741.1	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB750K5-525AXSP04	-	409.8	304.4	348.6	711.3	-	415	311.2	353.3	708.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB750K5-425AXSP04	-	373.4	275.7	316.5	655.7	228.6	378.3	281.7	321.5	654.1	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB370C4-625AXSP04	-	377.7	-	-	643.6	-	381.2	-	-	639.9	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB370C4-525AXSP04	-	357.6	-	304.2	616.8	-	360.8	-	308.2	613.1	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB370C4-425AXSP04	-	326	241.1	277.1	569.7	-	329.6	246.3	280.3	567.6	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB550C4-625AXSP04	-	426.1	-	363.6	730.9	-	430.6	-	368.2	727.2	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB550C4-525AXSP04	-	401.8	298.7	341.9	696.6	-	406.2	304.9	346	693.2	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB550C4-425AXSP04	-	364.6	269.3	309.3	640.2	-	368.7	275.4	313.6	637.6	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB750C4-625AXSP04	-	449.6	-	383.2	771.6	-	454.9	343.3	388.6	768.5	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB750C4-525AXSP04	-	424.3	315.1	361.1	737.7	-	430	322	366.3	734.5	606	17.3	4"	484	14.3	3"	727	24.4	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S4PB750C4-425AXSP04	226.20	386.2	285.3	327.6	679.5	236.3	391.4	291.4	332.3	677	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB370C5-625AXSP04	-	377.7	-	-	643.6	-	381.2	-	-	639.9	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB370C5-525AXSP04	-	357.6	-	304.2	616.8	-	360.8	-	308.2	613.1	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB370C5-425AXSP04	-	326	241.1	277.1	569.7	-	329.6	246.3	280.3	567.6	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB550C5-625AXSP04	-	426.1	-	363.6	730.9	-	430.6	-	368.2	727.2	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB550C5-525AXSP04	-	401.8	298.7	341.9	696.6	-	406.2	304.9	346	693.2	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB550C5-425AXSP04	-	364.6	269.3	309.3	640.2	-	368.7	275.4	313.6	637.6	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB750C5-625AXSP04	-	449.6	-	383.2	771.6	-	454.9	343.3	388.6	768.5	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB750C5-525AXSP04	-	424.3	315.1	361.1	737.7	-	430	322	366.3	734.5	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB750C5-425AXSP04	226.20	386.2	285.3	327.6	679.5	236.3	391.4	291.4	332.3	677	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB370K8-625AXSP04	-	363.1	-	-	617.9	-	366.4	-	-	613.7	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB370K8-525AXSP04	-	343.5	-	292.6	591.7	-	347	-	296.2	587.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB370K8-425AXSP04	-	314.1	232.4	266.8	547.7	-	317.3	237.2	270.2	545.4	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB550K8-625AXSP04	-	404.6	-	345.1	691.9	-	408.6	-	349.8	688.1	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB550K8-525AXSP04	-	381.9	284.2	324.9	660.7	-	386	289.9	329.2	657.4	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB550K8-425AXSP04	-	348.3	257.6	295.4	609.9	-	352.1	263.2	299.4	607.5	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PB750K8-625AXSP04	-	433.7	-	369.9	744.3	-	439.2	-	375.4	741.1	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S4PB750K8-525AXSP04	-	409.8	304.4	348.6	711.3	-	415	311.2	353.3	708.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S4PB750K8-425AXSP04	-	373.4	275.7	316.5	655.7	228.6	378.3	281.7	321.5	654.1	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S5PB370K4-625AXSP04	-	467.6	354.8	401	783.4	-	468.6	358.5	403	776.1	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB370K4-525AXSP04	-	442.5	333.7	378.8	751	-	444.1	337.5	380.8	744.1	606	20.8	4"	484	16.6	3"	727	29.2	4"
EAW-VD15S5PB370K4-425AXSP02	-	-	-	-	642	-	-	-	-	644	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB550K4-625AXSP04	-	521	394.5	446.5	877.5	-	523	398.9	449	870.4	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB550K4-525AXSP02	-	-	-	-	775.5	-	-	-	-	778.9	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550K4-425AXSP02	-	-	-	-	712.9	-	-	-	-	716.7	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB750K4-625AXSP04	346.50	558.8	422.7	478.9	943.1	356.2	562.3	428.6	482.1	937.6	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB750K4-525AXSP02	-	-	-	-	833.6	-	-	-	-	838.7	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750K4-425AXSP02	-	-	-	-	766.2	-	-	-	-	770.4	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB370K5-625AXSP04	-	467.6	354.8	401	783.4	-	468.6	358.5	403	776.1	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB370K5-525AXSP04	-	442.5	333.7	378.8	751	-	444.1	337.5	380.8	744.1	606	20.8	4"	484	16.6	3"	727	29.2	4"
EAW-VD15S5PB370K5-425AXSP02	-	-	-	-	642	-	-	-	-	644	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB550K5-625AXSP04	-	521	394.5	446.5	877.5	-	523	398.9	449	870.4	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB550K5-525AXSP02	-	-	-	-	775.5	-	-	-	-	778.9	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550K5-425AXSP02	-	-	-	-	712.9	-	-	-	-	716.7	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB750K5-625AXSP04	346.50	558.8	422.7	478.9	943.1	356.2	562.3	428.6	482.1	937.6	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB750K5-525AXSP02	-	-	-	-	833.6	-	-	-	-	838.7	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750K5-425AXSP02	-	-	-	-	766.2	-	-	-	-	770.4	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB370C4-625AXSP04	-	486.7	368.8	417	816	-	488.3	372.7	419.1	809.3	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB370C4-525AXSP04	283.30	460.8	347	394.1	782.1	291	462.7	351.1	395.9	776.1	606	20.8	4"	484	16.6	3"	727	29.2	4"
EAW-VD15S5PB370C4-425AXSP02	-	-	-	-	667.1	-	-	-	-	669.7	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB550C4-625AXSP04	340.70	549.7	415.5	470.6	926	350	551.3	420.4	473.5	918.9	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB550C4-525AXSP02	-	-	-	-	816.8	-	-	-	-	820.6	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550C4-425AXSP02	-	-	-	-	747.4	-	-	-	-	751.5	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB750C4-625AXSP04	358.10	578.7	437.2	495.6	977.8	368.5	582.7	443.6	499.2	972.4	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB750C4-525AXSP02	-	-	-	-	865	-	-	-	-	869.8	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750C4-425AXSP02	-	-	-	-	793.3	-	-	-	-	797.9	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB370C5-625AXSP04	-	486.7	368.8	417	816	-	488.3	372.7	419.1	809.3	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB370C5-525AXSP04	283.30	460.8	347	394.1	782.1	291	462.7	351.1	395.9	776.1	606	20.8	4"	484	16.6	3"	727	29.2	4"
EAW-VD15S5PB370C5-425AXSP02	-	-	-	-	667.1	-	-	-	-	669.7	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB550C5-625AXSP04	340.70	549.7	415.5	470.6	926	350	551.3	420.4	473.5	918.9	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB550C5-525AXSP02	-	-	-	-	816.8	-	-	-	-	820.6	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550C5-425AXSP02	-	-	-	-	747.4	-	-	-	-	751.5	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB750C5-625AXSP04	358.10	578.7	437.2	495.6	977.8	368.5	582.7	443.6	499.2	972.4	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB750C5-525AXSP02	-	-	-	-	865	-	-	-	-	869.8	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750C5-425AXSP02	-	-	-	-	793.3	-	-	-	-	797.9	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB370K8-625AXSP04	-	467.6	354.8	401	783.4	-	468.6	358.5	403	776.1	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB370K8-525AXSP04	-	442.5	333.7	378.8	751	-	444.1	337.5	380.8	744.1	606	20.8	4"	484	16.6	3"	727	29.2	4"
EAW-VD15S5PB370K8-425AXSP02	-	-	-	-	642	-	-	-	-	644	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB550K8-625AXSP04	-	521	394.5	446.5	877.5	-	523	398.9	449	870.4	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB550K8-525AXSP02	-	-	-	-	775.5	-	-	-	-	778.9	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550K8-425AXSP02	-	-	-	-	712.9	-	-	-	-	716.7	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S5PB750K8-625AXSP04	346.50	558.8	422.7	478.9	943.1	356.2	562.3	428.6	482.1	937.6	727	21.8	4"	581	14.4	4"	872	30.6	4"
EAW-VD15S5PB750K8-525AXSP02	-	-	-	-	833.6	-	-	-	-	838.7	1211	11.5	(2) 4"	969	7.6	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750K8-425AXSP02	-	-	-	-	766.2	-	-	-	-	770.4	969	10.7	(2) 4"	775	9.7	4"	1163	15	(2) 4"
EAW-VD15S6PB370K4-625AXSP02	-	-	-	-	894	-	-	-	-	892.7	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB370K4-525AXSP02	-	-	-	-	853.3	-	-	-	-	851.7	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB370K4-425AXSP02	-	-	-	-	787.1	-	-	-	-	786.7	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB550K4-625AXSP02	-	-	-	-	1000	-	-	-	-	998.8	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB550K4-525AXSP02	-	-	-	-	951.6	-	-	-	-	951.4	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB550K4-425AXSP02	-	482.5	-	-	874.8	-	495.3	-	-	876.2	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB750K4-625AXSP02	-	-	-	-	1073.7	-	-	-	-	1075	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB750K4-525AXSP02	-	569.9	-	-	1023.5	-	584.2	-	-	1024.8	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB750K4-425AXSP02	-	517.9	-	-	940.8	-	531.1	-	448.3	942.4	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB370K5-625AXSP02	-	-	-	-	894	-	-	-	-	892.7	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB370K5-525AXSP02	-	-	-	-	853.3	-	-	-	-	851.7	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB370K5-425AXSP02	-	-	-	-	787.1	-	-	-	-	786.7	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB550K5-625AXSP02	-	-	-	-	1000	-	-	-	-	998.8	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB550K5-525AXSP02	-	-	-	-	951.6	-	-	-	-	951.4	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB550K5-425AXSP02	-	482.5	-	-	874.8	-	495.3	-	-	876.2	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB750K5-625AXSP02	-	-	-	-	1073.7	-	-	-	-	1075	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB750K5-525AXSP02	-	569.9	-	-	1023.5	-	584.2	-	-	1024.8	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB750K5-425AXSP02	-	517.9	-	-	940.8	-	531.1	-	448.3	942.4	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB370C4-625AXSP02	-	-	-	-	930.8	-	-	-	-	930.5	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB370C4-525AXSP02	-	-	-	-	889.2	-	-	-	-	887.9	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB370C4-425AXSP02	-	451.9	-	-	818.1	-	463.7	-	-	818.3	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB550C4-625AXSP02	-	-	-	-	1054.5	-	-	-	-	1055.1	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB550C4-525AXSP02	-	-	-	-	1002.7	-	572.1	-	-	1002.6	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB550C4-425AXSP02	-	505.1	-	-	917.6	-	517.9	-	-	919	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB750C4-625AXSP02	-	-	-	-	1112.6	-	-	-	-	1114.4	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB750C4-525AXSP02	-	589.3	-	-	1060.8	-	605.8	-	-	1061.6	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB750C4-425AXSP02	-	534.9	-	449.7	974.4	-	549.9	-	463.4	976.3	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB370C5-625AXSP02	-	-	-	-	930.8	-	-	-	-	930.5	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB370C5-525AXSP02	-	-	-	-	889.2	-	-	-	-	887.9	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB370C5-425AXSP02	-	451.9	-	-	818.1	-	463.7	-	-	818.3	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB550C5-625AXSP02	-	-	-	-	1054.5	-	-	-	-	1055.1	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB550C5-525AXSP02	-	-	-	-	1002.7	-	572.1	-	-	1002.6	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB550C5-425AXSP02	-	505.1	-	-	917.6	-	517.9	-	-	919	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB750C5-625AXSP02	-	-	-	-	1112.6	-	-	-	-	1114.4	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB750C5-525AXSP02	-	589.3	-	-	1060.8	-	605.8	-	-	1061.6	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB750C5-425AXSP02	-	534.9	-	449.7	974.4	-	549.9	-	463.4	976.3	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB370K8-625AXSP02	-	-	-	-	894	-	-	-	-	892.7	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6PB370K8-525AXSP02	-	-	-	-	853.3	-	-	-	-	851.7	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB370K8-425AXSP02	-	-	-	-	787.1	-	-	-	-	786.7	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB550K8-625AXSP02	-	-	-	-	1000	-	-	-	-	998.8	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB550K8-525AXSP02	-	-	-	-	951.6	-	-	-	-	951.4	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB550K8-425AXSP02	-	482.5	-	-	874.8	-	495.3	-	-	876.2	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S6PB750K8-625AXSP02	-	-	-	-	1073.7	-	-	-	-	1075	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD15S6PB750K8-525AXSP02	-	569.9	-	-	1023.5	-	584.2	-	-	1024.8	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD15S6PB750K8-425AXSP02	-	517.9	-	-	940.8	-	531.1	-	448.3	942.4	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD15S1PK370K4-625AXSP16	-	98.2	-	84.2	165.1	-	98.6	-	84.7	163.4	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK370K4-525AXSP16	-	91.1	68.5	77.9	155.6	-	91.6	69.4	78.5	154.2	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK370K4-425AXSP16	-	85	63.6	72.5	146.7	-	85.5	64.4	73.1	145.4	121	24.5	1-1/2"	97	16.2	1-1/2"	145	30.7	2"
EAW-VD15S1PK550K4-625AXSP16	-	109.9	-	94.1	185.5	-	110.6	84.1	94.7	184	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK550K4-525AXSP16	-	101.8	76.2	86.9	174.2	-	102.4	77.4	87.6	173.1	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK550K4-425AXSP12	-	88.9	-	75	157.8	-	90.4	-	76.6	157.4	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK750K4-625AXSP16	-	118.5	89.3	101.3	200.7	-	119.3	90.6	102.2	199.3	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK750K4-525AXSP12	-	104.4	-	-	183.8	-	106.2	-	90.1	183.2	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK750K4-425AXSP12	-	95.7	-	80.8	170.5	-	97.4	-	82.6	170.1	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK370K5-625AXSP16	-	98.2	-	84.2	165.1	-	98.6	-	84.7	163.4	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK370K5-525AXSP16	-	91.1	68.5	77.9	155.6	-	91.6	69.4	78.5	154.2	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK370K5-425AXSP16	-	85	63.6	72.5	146.7	-	85.5	64.4	73.1	145.4	121	24.5	1-1/2"	97	16.2	1-1/2"	145	30.7	2"
EAW-VD15S1PK550K5-625AXSP16	-	109.9	-	94.1	185.5	-	110.6	84.1	94.7	184	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK550K5-525AXSP16	-	101.8	76.2	86.9	174.2	-	102.4	77.4	87.6	173.1	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK550K5-425AXSP12	-	88.9	-	75	157.8	-	90.4	-	76.6	157.4	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK750K5-625AXSP16	-	118.5	89.3	101.3	200.7	-	119.3	90.6	102.2	199.3	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK750K5-525AXSP12	-	104.4	-	-	183.8	-	106.2	-	90.1	183.2	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK750K5-425AXSP12	-	95.7	-	80.8	170.5	-	97.4	-	82.6	170.1	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK370C4-625AXSP16	-	102.4	-	87.7	172.4	-	102.9	-	88.3	170.8	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK370C4-525AXSP16	-	95	71.2	81.1	162.1	-	95.5	72.2	81.7	160.9	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK370C4-425AXSP16	-	88.5	66	75.3	152.7	-	89	66.9	75.9	151.6	121	24.5	1-1/2"	97	16.2	1-1/2"	145	30.7	2"
EAW-VD15S1PK550C4-625AXSP16	-	116	87.4	99.3	196.2	-	116.6	88.7	100	194.6	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK550C4-525AXSP12	-	101.8	-	-	179.2	-	103.5	-	-	178.6	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK550C4-425AXSP12	-	93	-	78.5	165.5	-	94.6	-	80.1	164.9	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK750C4-625AXSP16	-	123	92.7	105.1	208.7	-	123.8	94.1	106.1	207.4	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK750C4-525AXSP12	-	108.2	-	91.6	190.8	-	110.1	-	93.5	190.2	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK750C4-425AXSP12	-	99	-	83.6	176.5	-	100.6	74.4	85.2	176.1	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK370C5-625AXSP16	-	102.4	-	87.7	172.4	-	102.9	-	88.3	170.8	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK370C5-525AXSP16	-	95	71.2	81.1	162.1	-	95.5	72.2	81.7	160.9	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK370C5-425AXSP16	-	88.5	66	75.3	152.7	-	89	66.9	75.9	151.6	121	24.5	1-1/2"	97	16.2	1-1/2"	145	30.7	2"
EAW-VD15S1PK550C5-625AXSP16	-	116	87.4	99.3	196.2	-	116.6	88.7	100	194.6	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK550C5-525AXSP12	-	101.8	-	-	179.2	-	103.5	-	-	178.6	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK550C5-425AXSP12	-	93	-	78.5	165.5	-	94.6	-	80.1	164.9	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK750C5-625AXSP16	-	123	92.7	105.1	208.7	-	123.8	94.1	106.1	207.4	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK750C5-525AXSP12	-	108.2	-	91.6	190.8	-	110.1	-	93.5	190.2	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK750C5-425AXSP12	-	99	-	83.6	176.5	-	100.6	74.4	85.2	176.1	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK370K8-625AXSP16	-	98.2	-	84.2	165.1	-	98.6	-	84.7	163.4	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK370K8-525AXSP16	-	91.1	68.5	77.9	155.6	-	91.6	69.4	78.5	154.2	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK370K8-425AXSP16	-	85	63.6	72.5	146.7	-	85.5	64.4	73.1	145.4	121	24.5	1-1/2"	97	16.2	1-1/2"	145	30.7	2"
EAW-VD15S1PK550K8-625AXSP16	-	109.9	-	94.1	185.5	-	110.6	84.1	94.7	184	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK550K8-525AXSP16	-	101.8	76.2	86.9	174.2	-	102.4	77.4	87.6	173.1	145	22.5	2"	116	17.3	1-1/2"	174	31.6	2"
EAW-VD15S1PK550K8-425AXSP12	-	88.9	-	75	157.8	-	90.4	-	76.6	157.4	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S1PK750K8-625AXSP16	-	118.5	89.3	101.3	200.7	-	119.3	90.6	102.2	199.3	182	23.7	2"	145	15.6	2"	218	33.3	2"
EAW-VD15S1PK750K8-525AXSP12	-	104.4	-	-	183.8	-	106.2	-	90.1	183.2	194	19	2"	155	12.5	2"	232	26.7	2"
EAW-VD15S1PK750K8-425AXSP12	-	95.7	-	80.8	170.5	-	97.4	-	82.6	170.1	157	17.7	2"	126	14.5	1-1/2"	189	24.9	2"
EAW-VD15S2PK370K4-625AXSP08	-	195.7	-	-	329.2	-	196.6	-	168.8	326.1	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK370K4-525AXSP08	-	185.1	-	158.3	315.4	-	186.3	141.2	159.5	312.6	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK370K4-425AXSP08	-	169.3	126.5	144.2	292.2	-	170.3	128.2	145.4	290.1	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK550K4-625AXSP08	-	219.2	-	187.4	370.1	-	220.3	-	189	367.2	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK550K4-525AXSP08	-	206.9	155.3	176.5	353.8	-	208.3	157.4	178.1	351.1	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK550K4-425AXSP08	113.10	188.7	140.5	160.6	326.6	116.9	189.9	142.8	162	324.6	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK750K4-625AXSP08	-	236	177.9	202	399.9	-	237.6	180.5	203.5	397.2	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK750K4-525AXSP08	-	222.8	166.9	190	382.2	-	224.4	169.6	191.8	379.8	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK750K4-425AXSP06	-	190.1	-	160.6	338.9	-	193.5	-	164	338.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PK370K5-625AXSP08	-	195.7	-	-	329.2	-	196.6	-	168.8	326.1	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK370K5-525AXSP08	-	185.1	-	158.3	315.4	-	186.3	141.2	159.5	312.6	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK370K5-425AXSP08	-	169.3	126.5	144.2	292.2	-	170.3	128.2	145.4	290.1	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK550K5-625AXSP08	-	219.2	-	187.4	370.1	-	220.3	-	189	367.2	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK550K5-525AXSP08	-	206.9	155.3	176.5	353.8	-	208.3	157.4	178.1	351.1	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK550K5-425AXSP08	113.10	188.7	140.5	160.6	326.6	116.9	189.9	142.8	162	324.6	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK750K5-625AXSP08	-	236	177.9	202	399.9	-	237.6	180.5	203.5	397.2	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK750K5-525AXSP08	-	222.8	166.9	190	382.2	-	224.4	169.6	191.8	379.8	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK750K5-425AXSP06	-	190.1	-	160.6	338.9	-	193.5	-	164	338.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PK370C4-625AXSP08	-	204	-	174.7	344	-	205.1	-	175.9	340.9	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK370C4-525AXSP08	-	192.9	145	164.9	329.1	-	194	147	166.1	326.3	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK370C4-425AXSP08	-	176.1	131.3	149.9	304.1	-	177.2	133.2	151.2	301.9	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK550C4-625AXSP08	-	231.1	174	197.7	391.4	-	232.4	176.6	199.1	388.3	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK550C4-525AXSP08	-	217.4	162.8	185.6	372.6	-	218.9	165.4	187	369.6	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK550C4-425AXSP06	-	184.6	-	155.8	329	-	187.8	-	159.1	328.3	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PK750C4-625AXSP08	-	245.1	184.5	209.4	415.8	-	246.9	187.3	211.4	413.3	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK750C4-525AXSP08	-	231	173.1	197.2	397	144.5	232.8	175.7	198.8	394.5	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK750C4-425AXSP06	-	196.6	-	165.8	350.8	-	200.2	147.8	169.5	350.1	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PK370C5-625AXSP08	-	204	-	174.7	344	-	205.1	-	175.9	340.9	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK370C5-525AXSP08	-	192.9	145	164.9	329.1	-	194	147	166.1	326.3	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK370C5-425AXSP08	-	176.1	131.3	149.9	304.1	-	177.2	133.2	151.2	301.9	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK550C5-625AXSP08	-	231.1	174	197.7	391.4	-	232.4	176.6	199.1	388.3	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK550C5-525AXSP08	-	217.4	162.8	185.6	372.6	-	218.9	165.4	187	369.6	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK550C5-425AXSP06	-	184.6	-	155.8	329	-	187.8	-	159.1	328.3	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PK750C5-625AXSP08	-	245.1	184.5	209.4	415.8	-	246.9	187.3	211.4	413.3	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK750C5-525AXSP08	-	231	173.1	197.2	397	144.5	232.8	175.7	198.8	394.5	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK750C5-425AXSP06	-	196.6	-	165.8	350.8	-	200.2	147.8	169.5	350.1	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S2PK370K8-625AXSP08	-	195.7	-	-	329.2	-	196.6	-	168.8	326.1	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK370K8-525AXSP08	-	185.1	-	158.3	315.4	-	186.3	141.2	159.5	312.6	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK370K8-425AXSP08	-	169.3	126.5	144.2	292.2	-	170.3	128.2	145.4	290.1	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK550K8-625AXSP08	-	219.2	-	187.4	370.1	-	220.3	-	189	367.2	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK550K8-525AXSP08	-	206.9	155.3	176.5	353.8	-	208.3	157.4	178.1	351.1	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK550K8-425AXSP08	113.10	188.7	140.5	160.6	326.6	116.9	189.9	142.8	162	324.6	242	19	3"	194	15.5	2"	291	26.7	3"
EAW-VD15S2PK750K8-625AXSP08	-	236	177.9	202	399.9	-	237.6	180.5	203.5	397.2	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD15S2PK750K8-525AXSP08	-	222.8	166.9	190	382.2	-	224.4	169.6	191.8	379.8	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD15S2PK750K8-425AXSP06	-	190.1	-	160.6	338.9	-	193.5	-	164	338.2	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD15S3PK370K4-625AXSP06	-	296.9	225.7	254.9	496	-	297.5	227.7	255.8	490.8	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK370K4-525AXSP06	-	280	211.3	239.6	473.7	-	280.6	213.4	240.6	468.9	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK370K4-425AXSP04	-	239.8	-	-	424.8	-	243.6	-	-	423.1	484	17.1	3"	388	11.3	3"	581	20	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PK550K4-625AXSP06	-	332.6	252.1	285	557.8	-	333.4	254.8	286.5	552.7	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK550K4-525AXSP06	192.30	312.5	235.5	267.2	530.7	197.5	313.8	238	268.8	526.6	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK550K4-425AXSP04	-	266.7	-	225.5	474.9	-	271.6	-	230.1	473.7	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK750K4-625AXSP06	-	358.3	271.6	307	602.8	228.8	359.6	274.6	308.7	598.7	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK750K4-525AXSP04	-	315.7	-	-	556.7	-	321.5	-	-	554.8	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK750K4-425AXSP04	-	287.2	-	242.7	512.3	-	292.8	-	247.8	512	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK370K5-625AXSP06	-	296.9	225.7	254.9	496	-	297.5	227.7	255.8	490.8	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK370K5-525AXSP06	-	280	211.3	239.6	473.7	-	280.6	213.4	240.6	468.9	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK370K5-425AXSP04	-	239.8	-	-	424.8	-	243.6	-	-	423.1	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK550K5-625AXSP06	-	332.6	252.1	285	557.8	-	333.4	254.8	286.5	552.7	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK550K5-525AXSP06	192.30	312.5	235.5	267.2	530.7	197.5	313.8	238	268.8	526.6	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK550K5-425AXSP04	-	266.7	-	225.5	474.9	-	271.6	-	230.1	473.7	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK750K5-625AXSP06	-	358.3	271.6	307	602.8	228.8	359.6	274.6	308.7	598.7	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK750K5-525AXSP04	-	315.7	-	-	556.7	-	321.5	-	-	554.8	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK750K5-425AXSP04	-	287.2	-	242.7	512.3	-	292.8	-	247.8	512	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK370C4-625AXSP06	-	310	235.4	266	518.4	-	310.4	237.6	267	513.1	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK370C4-525AXSP06	-	291.4	220.2	249.5	493.7	-	292.2	222.1	250.6	489.4	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK370C4-425AXSP04	-	249.3	-	-	442.6	-	253.4	-	-	440.9	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK550C4-625AXSP06	-	350.8	265.8	300.7	589.9	-	351.7	268.3	302	584.5	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK550C4-525AXSP04	-	308.3	-	-	542.8	-	313.3	-	-	540.9	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK550C4-425AXSP04	-	278.9	-	235.5	497.4	-	284.2	-	240.8	496.1	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK750C4-625AXSP06	231.10	372.1	281.7	318.6	626.7	237.1	373.8	284.7	320.7	622.1	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK750C4-525AXSP04	-	327.7	-	-	578	-	333.3	-	283.3	576.2	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK750C4-425AXSP04	-	297.1	-	250.8	530.3	-	302.4	-	256.2	530	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK370C5-625AXSP06	-	310	235.4	266	518.4	-	310.4	237.6	267	513.1	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK370C5-525AXSP06	-	291.4	220.2	249.5	493.7	-	292.2	222.1	250.6	489.4	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK370C5-425AXSP04	-	249.3	-	-	442.6	-	253.4	-	-	440.9	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK550C5-625AXSP06	-	350.8	265.8	300.7	589.9	-	351.7	268.3	302	584.5	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK550C5-525AXSP04	-	308.3	-	-	542.8	-	313.3	-	-	540.9	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK550C5-425AXSP04	-	278.9	-	235.5	497.4	-	284.2	-	240.8	496.1	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK750C5-625AXSP06	231.10	372.1	281.7	318.6	626.7	237.1	373.8	284.7	320.7	622.1	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK750C5-525AXSP04	-	327.7	-	-	578	-	333.3	-	283.3	576.2	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK750C5-425AXSP04	-	297.1	-	250.8	530.3	-	302.4	-	256.2	530	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK370K8-625AXSP06	-	296.9	225.7	254.9	496	-	297.5	227.7	255.8	490.8	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK370K8-525AXSP06	-	280	211.3	239.6	473.7	-	280.6	213.4	240.6	468.9	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK370K8-425AXSP04	-	239.8	-	-	424.8	-	243.6	-	-	423.1	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK550K8-625AXSP06	-	332.6	252.1	285	557.8	-	333.4	254.8	286.5	552.7	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK550K8-525AXSP06	192.30	312.5	235.5	267.2	530.7	197.5	313.8	238	268.8	526.6	400	22.2	3"	320	14.6	3"	480	31.2	3"
EAW-VD15S3PK550K8-425AXSP04	-	266.7	-	225.5	474.9	-	271.6	-	230.1	473.7	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S3PK750K8-625AXSP06	-	358.3	271.6	307	602.8	228.8	359.6	274.6	308.7	598.7	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD15S3PK750K8-525AXSP04	-	315.7	-	-	556.7	-	321.5	-	-	554.8	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD15S3PK750K8-425AXSP04	-	287.2	-	242.7	512.3	-	292.8	-	247.8	512	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD15S4PK370K4-625AXSP04	-	388.4	-	-	654.5	-	390.3	-	-	649.3	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK370K4-525AXSP04	-	367.7	-	313.9	626.9	-	369.6	-	316.2	621.3	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK370K4-425AXSP04	-	335.8	250.2	285.5	580.3	-	337.9	254.1	287.9	575.3	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK550K4-625AXSP04	-	434.9	-	372.1	735.8	-	437.2	-	374.9	730	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK550K4-525AXSP04	-	410.1	307.5	350.3	703.1	-	413.1	311.9	353	697.7	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK550K4-425AXSP04	-	373.7	278.4	317.8	648.4	231.2	376.2	282.4	320.7	644.6	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK750K4-625AXSP04	-	468.8	352.5	400.6	795	-	472.1	358.3	404.2	789.7	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK750K4-525AXSP04	-	441.6	330.5	377	759.3	-	445.6	335.9	380.7	754.6	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK750K4-425AXSP02	-	-	-	-	638.7	-	-	-	-	643.4	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD15S4PK370K5-625AXSP04	-	388.4	-	-	654.5	-	390.3	-	-	649.3	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK370K5-525AXSP04	-	367.7	-	313.9	626.9	-	369.6	-	316.2	621.3	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK370K5-425AXSP04	-	335.8	250.2	285.5	580.3	-	337.9	254.1	287.9	575.3	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK550K5-625AXSP04	-	434.9	-	372.1	735.8	-	437.2	-	374.9	730	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK550K5-525AXSP04	-	410.1	307.5	350.3	703.1	-	413.1	311.9	353	697.7	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK550K5-425AXSP04	-	373.7	278.4	317.8	648.4	231.2	376.2	282.4	320.7	644.6	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK750K5-625AXSP04	-	468.8	352.5	400.6	795	-	472.1	358.3	404.2	789.7	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK750K5-525AXSP04	-	441.6	330.5	377	759.3	-	445.6	335.9	380.7	754.6	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK750K5-425AXSP02	-	-	-	-	638.7	-	-	-	-	643.4	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD15S4PK370C4-625AXSP04	-	405.5	-	346.9	683.9	-	407.6	-	349.5	677.9	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK370C4-525AXSP04	-	382.5	287.2	326.7	654.1	-	384.8	291.2	329.3	648.5	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK370C4-425AXSP04	-	348.8	259.8	297.2	603.9	-	351.1	264	299.4	599.7	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK550C4-625AXSP04	-	458.5	345	391.9	778.1	-	461.7	350.2	395.5	771.9	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK550C4-525AXSP04	-	431	322.9	367.6	740.3	-	434.1	327.6	371.1	734.5	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK550C4-425AXSP04	233.60	391.3	290.7	332.3	679.4	241.2	393.9	295	335.3	675.3	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK750C4-625AXSP04	-	486.1	365.5	415.7	826.5	-	490	371.4	419.8	821.6	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK750C4-525AXSP04	-	458.6	342.7	390.6	788.6	285.9	462.2	347.9	394.5	783.8	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK750C4-425AXSP02	-	-	-	-	660.5	-	-	-	-	665.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD15S4PK370C5-625AXSP04	-	405.5	-	346.9	683.9	-	407.6	-	349.5	677.9	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK370C5-525AXSP04	-	382.5	287.2	326.7	654.1	-	384.8	291.2	329.3	648.5	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK370C5-425AXSP04	-	348.8	259.8	297.2	603.9	-	351.1	264	299.4	599.7	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK550C5-625AXSP04	-	458.5	345	391.9	778.1	-	461.7	350.2	395.5	771.9	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK550C5-525AXSP04	-	431	322.9	367.6	740.3	-	434.1	327.6	371.1	734.5	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK550C5-425AXSP04	233.60	391.3	290.7	332.3	679.4	241.2	393.9	295	335.3	675.3	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK750C5-625AXSP04	-	486.1	365.5	415.7	826.5	-	490	371.4	419.8	821.6	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK750C5-525AXSP04	-	458.6	342.7	390.6	788.6	285.9	462.2	347.9	394.5	783.8	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK750C5-425AXSP02	-	-	-	-	660.5	-	-	-	-	665.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD15S4PK370K8-625AXSP04	-	388.4	-	-	654.5	-	390.3	-	-	649.3	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK370K8-525AXSP04	-	367.7	-	313.9	626.9	-	369.6	-	316.2	621.3	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK370K8-425AXSP04	-	335.8	250.2	285.5	580.3	-	337.9	254.1	287.9	575.3	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK550K8-625AXSP04	-	434.9	-	372.1	735.8	-	437.2	-	374.9	730	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK550K8-525AXSP04	-	410.1	307.5	350.3	703.1	-	413.1	311.9	353	697.7	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK550K8-425AXSP04	-	373.7	278.4	317.8	648.4	231.2	376.2	282.4	320.7	644.6	484	21	3"	388	13.8	3"	581	25.4	4"
EAW-VD15S4PK750K8-625AXSP04	-	468.8	352.5	400.6	795	-	472.1	358.3	404.2	789.7	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD15S4PK750K8-525AXSP04	-	441.6	330.5	377	759.3	-	445.6	335.9	380.7	754.6	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD15S4PK750K8-425AXSP02	-	-	-	-	638.7	-	-	-	-	643.4	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD15S5PK370K4-625AXSP04	-	498.6	380.4	428.3	828.6	-	498.3	382.6	429.2	819	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK370K4-525AXSP02	-	-	-	-	741.4	-	-	-	-	741.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK370K4-425AXSP02	-	-	-	-	683.6	-	-	-	-	683.3	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK550K4-625AXSP04	351.60	558	425	479	931.9	358.3	558.5	427.6	480.1	922.2	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK550K4-525AXSP02	-	-	-	-	829.9	-	-	-	-	831	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK550K4-425AXSP02	-	-	-	-	763	-	-	-	-	764	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK750K4-625AXSP02	-	-	-	-	943.1	-	-	-	-	943.5	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK750K4-525AXSP02	-	-	-	-	896.3	-	-	-	-	897.6	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK750K4-425AXSP02	-	448.2	-	-	823.4	-	462.5	-	-	824.9	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK370K5-625AXSP04	-	498.6	380.4	428.3	828.6	-	498.3	382.6	429.2	819	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK370K5-525AXSP02	-	-	-	-	741.4	-	-	-	-	741.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK370K5-425AXSP02	-	-	-	-	683.6	-	-	-	-	683.3	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK550K5-625AXSP04	351.60	558	425	479	931.9	358.3	558.5	427.6	480.1	922.2	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK550K5-525AXSP02	-	-	-	-	829.9	-	-	-	-	831	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S5PK550K5-425AXSP02	-	-	-	-	763	-	-	-	-	764	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK750K5-625AXSP02	-	-	-	-	943.1	-	-	-	-	943.5	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK750K5-525AXSP02	-	-	-	-	896.3	-	-	-	-	897.6	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK750K5-425AXSP02	-	448.2	-	-	823.4	-	462.5	-	-	824.9	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK370C4-625AXSP04	-	520	396.3	446.9	865.9	-	519.9	398.8	447.4	856.1	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK370C4-525AXSP02	-	-	-	-	773	-	-	-	-	773.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK370C4-425AXSP02	-	-	-	-	710.7	-	-	-	-	710.7	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK550C4-625AXSP02	-	-	-	-	922.1	-	-	-	-	922.4	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK550C4-525AXSP02	-	-	-	-	874.2	-	-	-	-	874.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK550C4-425AXSP02	-	-	-	-	798.5	-	448.5	-	-	799.7	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK750C4-625AXSP02	-	-	-	-	978.7	-	-	-	-	981.1	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK750C4-525AXSP02	-	-	-	-	930.2	-	-	-	-	931.8	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK750C4-425AXSP02	-	464.2	-	-	852	-	478.2	-	-	853.6	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK370C5-625AXSP04	-	520	396.3	446.9	865.9	-	519.9	398.8	447.4	856.1	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK370C5-525AXSP02	-	-	-	-	773	-	-	-	-	773.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK370C5-425AXSP02	-	-	-	-	710.7	-	-	-	-	710.7	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK550C5-625AXSP02	-	-	-	-	922.1	-	-	-	-	922.4	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK550C5-525AXSP02	-	-	-	-	874.2	-	-	-	-	874.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK550C5-425AXSP02	-	-	-	-	798.5	-	448.5	-	-	799.7	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK750C5-625AXSP02	-	-	-	-	978.7	-	-	-	-	981.1	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK750C5-525AXSP02	-	-	-	-	930.2	-	-	-	-	931.8	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK750C5-425AXSP02	-	464.2	-	-	852	-	478.2	-	-	853.6	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK370K8-625AXSP04	-	498.6	380.4	428.3	828.6	-	498.3	382.6	429.2	819	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK370K8-525AXSP02	-	-	-	-	741.4	-	-	-	-	741.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK370K8-425AXSP02	-	-	-	-	683.6	-	-	-	-	683.3	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK550K8-625AXSP04	351.60	558	425	479	931.9	358.3	558.5	427.6	480.1	922.2	727	23.7	4"	581	15.6	4"	872	33.3	4"
EAW-VD15S5PK550K8-525AXSP02	-	-	-	-	829.9	-	-	-	-	831	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK550K8-425AXSP02	-	-	-	-	763	-	-	-	-	764	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S5PK750K8-625AXSP02	-	-	-	-	943.1	-	-	-	-	943.5	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.9	(2) 4"
EAW-VD15S5PK750K8-525AXSP02	-	-	-	-	896.3	-	-	-	-	897.6	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.5	(2) 4"
EAW-VD15S5PK750K8-425AXSP02	-	448.2	-	-	823.4	-	462.5	-	-	824.9	969	11.6	(2) 4"	775	10.4	4"	1163	16.4	(2) 4"
EAW-VD15S6PK370K4-625AXSP02	-	-	-	-	951	-	-	-	-	946.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK370K4-525AXSP02	-	-	-	-	907.3	-	-	-	-	903.2	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK370K4-425AXSP02	-	469.1	-	-	836.2	-	477.8	-	-	833.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK550K4-625AXSP02	-	-	-	-	1067	-	-	-	-	1062.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK550K4-525AXSP02	-	575.6	-	-	1015	-	586.2	-	-	1013.2	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK550K4-425AXSP02	-	522.1	-	-	934.1	-	532.3	-	451	932.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK750K4-625AXSP02	-	-	-	-	1152	-	-	-	-	1149.2	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK750K4-525AXSP02	-	619.5	-	-	1096.7	-	631.3	-	-	1094.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK750K4-425AXSP02	-	562.9	-	474.3	1007.1	-	573.3	-	485.4	1006.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK370K5-625AXSP02	-	-	-	-	951	-	-	-	-	946.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK370K5-525AXSP02	-	-	-	-	907.3	-	-	-	-	903.2	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK370K5-425AXSP02	-	469.1	-	-	836.2	-	477.8	-	-	833.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK550K5-625AXSP02	-	-	-	-	1067	-	-	-	-	1062.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK550K5-525AXSP02	-	575.6	-	-	1015	-	586.2	-	-	1013.2	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK550K5-425AXSP02	-	522.1	-	-	934.1	-	532.3	-	451	932.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK750K5-625AXSP02	-	-	-	-	1152	-	-	-	-	1149.2	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK750K5-525AXSP02	-	619.5	-	-	1096.7	-	631.3	-	-	1094.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK750K5-425AXSP02	-	562.9	-	474.3	1007.1	-	573.3	-	485.4	1006.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK370C4-625AXSP02	-	-	-	-	992.2	-	-	-	-	988.6	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK370C4-525AXSP02	-	-	-	-	946.3	-	-	-	-	942.3	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK370C4-425AXSP02	-	488.3	-	-	869.7	-	496.8	-	-	868	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK550C4-625AXSP02	-	-	-	-	1127.6	-	-	-	-	1123.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK550C4-525AXSP02	-	604.1	-	-	1069.5	-	615.4	-	-	1066.1	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK550C4-425AXSP02	-	546.9	-	461	978	-	556.7	-	471	975.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK750C4-625AXSP02	-	683.1	-	-	1197.2	-	696.7	-	-	1195.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK750C4-525AXSP02	-	641.8	-	-	1138.5	-	654.4	-	-	1136.8	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK750C4-425AXSP02	-	581.1	-	490.5	1042.4	-	593.1	-	501.7	1042.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK370C5-625AXSP02	-	-	-	-	992.2	-	-	-	-	988.6	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK370C5-525AXSP02	-	-	-	-	946.3	-	-	-	-	942.3	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK370C5-425AXSP02	-	488.3	-	-	869.7	-	496.8	-	-	868	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK550C5-625AXSP02	-	-	-	-	1127.6	-	-	-	-	1123.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK550C5-525AXSP02	-	604.1	-	-	1069.5	-	615.4	-	-	1066.1	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK550C5-425AXSP02	-	546.9	-	461	978	-	556.7	-	471	975.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK750C5-625AXSP02	-	683.1	-	-	1197.2	-	696.7	-	-	1195.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK750C5-525AXSP02	-	641.8	-	-	1138.5	-	654.4	-	-	1136.8	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK750C5-425AXSP02	-	581.1	-	490.5	1042.4	-	593.1	-	501.7	1042.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK370K8-625AXSP02	-	-	-	-	951	-	-	-	-	946.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK370K8-525AXSP02	-	-	-	-	907.3	-	-	-	-	903.2	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK370K8-425AXSP02	-	469.1	-	-	836.2	-	477.8	-	-	833.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK550K8-625AXSP02	-	-	-	-	1067	-	-	-	-	1062.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK550K8-525AXSP02	-	575.6	-	-	1015	-	586.2	-	-	1013.2	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK550K8-425AXSP02	-	522.1	-	-	934.1	-	532.3	-	451	932.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S6PK750K8-625AXSP02	-	-	-	-	1152	-	-	-	-	1149.2	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S6PK750K8-525AXSP02	-	619.5	-	-	1096.7	-	631.3	-	-	1094.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S6PK750K8-425AXSP02	-	562.9	-	474.3	1007.1	-	573.3	-	485.4	1006.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S1PI370K4-625AXSP16	-	108.9	-	93.7	180.2	-	108.6	-	93.6	177.9	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI370K4-525AXSP16	-	101.1	76.7	86.7	169.8	-	101	77.1	86.7	167.9	145	25.6	2"	116	19.3	1-1/2"	174	36	2"
EAW-VD15S1PI370K4-425AXSP12	-	89.4	-	76	155	-	90.1	-	76.8	153.9	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI550K4-625AXSP16	-	122.9	93.6	105.5	204.1	-	122.7	94.2	105.6	201.8	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI550K4-525AXSP12	-	109.2	-	93	188.1	-	110.1	-	94	186.4	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI550K4-425AXSP12	-	100	74.2	85.1	174.4	-	101	75.6	85.9	173	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI750K4-625AXSP12	-	128.4	-	-	218.3	-	129.3	-	-	216.7	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD15S1PI750K4-525AXSP12	-	118.5	-	100.9	204.4	-	119.5	89.9	102	202.9	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI750K4-425AXSP12	-	108.4	80.3	91.9	189.1	-	109.4	81.8	93	187.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI370K5-625AXSP16	-	108.9	-	93.7	180.2	-	108.6	-	93.6	177.9	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI370K5-525AXSP16	-	101.1	76.7	86.7	169.8	-	101	77.1	86.7	167.9	145	25.6	2"	116	19.3	1-1/2"	174	36	2"
EAW-VD15S1PI370K5-425AXSP12	-	89.4	-	76	155	-	90.1	-	76.8	153.9	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI550K5-625AXSP16	-	122.9	93.6	105.5	204.1	-	122.7	94.2	105.6	201.8	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI550K5-525AXSP12	-	109.2	-	93	188.1	-	110.1	-	94	186.4	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI550K5-425AXSP12	-	100	74.2	85.1	174.4	-	101	75.6	85.9	173	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI750K5-625AXSP12	-	128.4	-	-	218.3	-	129.3	-	-	216.7	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD15S1PI750K5-525AXSP12	-	118.5	-	100.9	204.4	-	119.5	89.9	102	202.9	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI750K5-425AXSP12	-	108.4	80.3	91.9	189.1	-	109.4	81.8	93	187.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI370C4-625AXSP16	-	113.8	86.9	97.9	188.6	-	113.6	87.3	97.8	186.2	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI370C4-525AXSP12	-	101.4	-	-	173.9	-	102.1	-	-	172.5	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI370C4-425AXSP12	-	93	-	78.9	161.4	-	93.7	-	79.7	160.2	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI550C4-625AXSP12	-	124.6	-	-	211.7	-	125.4	-	-	209.7	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD15S1PI550C4-525AXSP12	-	114.5	-	97.6	197.6	-	115.4	-	98.6	195.8	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI550C4-425AXSP12	-	104.5	77.5	88.8	182.3	-	105.3	78.9	89.7	180.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI750C4-625AXSP12	-	133.3	-	113.8	227.3	-	134.5	-	115.1	225.5	242	18.8	3"	194	15.3	2"	291	26.3	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1PI750C4-525AXSP12	-	122.7	91.3	104.6	212.1	-	123.8	93.1	105.7	210.8	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI750C4-425AXSP12	-	112	83	95	195.8	-	113.1	84.5	96.2	194.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI370C5-625AXSP16	-	113.8	86.9	97.9	188.6	-	113.6	87.3	97.8	186.2	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI370C5-525AXSP12	-	101.4	-	-	173.9	-	102.1	-	-	172.5	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI370C5-425AXSP12	-	93	-	78.9	161.4	-	93.7	-	79.7	160.2	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI550C5-625AXSP12	-	124.6	-	-	211.7	-	125.4	-	-	209.7	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD15S1PI550C5-525AXSP12	-	114.5	-	97.6	197.6	-	115.4	-	98.6	195.8	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI550C5-425AXSP12	-	104.5	77.5	88.8	182.3	-	105.3	78.9	89.7	180.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI750C5-625AXSP12	-	133.3	-	113.8	227.3	-	134.5	-	115.1	225.5	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD15S1PI750C5-525AXSP12	-	122.7	91.3	104.6	212.1	-	123.8	93.1	105.7	210.8	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI750C5-425AXSP12	-	112	83	95	195.8	-	113.1	84.5	96.2	194.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI370K8-625AXSP16	-	108.9	-	93.7	180.2	-	108.6	-	93.6	177.9	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI370K8-525AXSP16	-	101.1	76.7	86.7	169.8	-	101	77.1	86.7	167.9	145	25.6	2"	116	19.3	1-1/2"	174	36	2"
EAW-VD15S1PI370K8-425AXSP12	-	89.4	-	76	155	-	90.1	-	76.8	153.9	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI550K8-625AXSP16	-	122.9	93.6	105.5	204.1	-	122.7	94.2	105.6	201.8	182	26.8	2"	145	17.7	2"	218	37.6	2"
EAW-VD15S1PI550K8-525AXSP12	-	109.2	-	93	188.1	-	110.1	-	94	186.4	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI550K8-425AXSP12	-	100	74.2	85.1	174.4	-	101	75.6	85.9	173	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S1PI750K8-625AXSP12	-	128.4	-	-	218.3	-	129.3	-	-	216.7	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD15S1PI750K8-525AXSP12	-	118.5	-	100.9	204.4	-	119.5	89.9	102	202.9	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD15S1PI750K8-425AXSP12	-	108.4	80.3	91.9	189.1	-	109.4	81.8	93	187.8	157	20.1	2"	126	16.1	1-1/2"	189	28.2	2"
EAW-VD15S2PI370K4-625AXSP08	-	217.2	-	186.6	359.6	-	216.7	-	186.7	355.1	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI370K4-525AXSP08	-	205.3	155.9	176.2	344.1	-	205.1	156.7	176.1	340.2	303	22.7	3"	242	15	3"	363	31.9	3"
EAW-VD15S2PI370K4-425AXSP06	-	177.8	-	151	308.8	-	179.1	-	152.8	306	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI550K4-625AXSP08	-	244.8	186.5	210.2	407.4	-	244.7	187.6	210.5	402.7	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI550K4-525AXSP06	-	220.7	-	187.8	379.5	-	222.3	-	189.9	376.2	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI550K4-425AXSP06	-	198.8	147.3	168.9	346.7	-	200.7	150.2	170.7	344.1	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI750K4-625AXSP08	-	265.7	202.2	228.1	443.4	170.4	265.7	203.6	228.5	439	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI750K4-525AXSP06	-	239.2	-	203.8	412.6	-	241.3	-	206.1	410	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI750K4-425AXSP06	-	215.3	159.4	182.8	376.5	-	217.3	162.3	184.8	374	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI370K5-625AXSP08	-	217.2	-	186.6	359.6	-	216.7	-	186.7	355.1	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI370K5-525AXSP08	-	205.3	155.9	176.2	344.1	-	205.1	156.7	176.1	340.2	303	22.7	3"	242	15	3"	363	31.9	3"
EAW-VD15S2PI370K5-425AXSP06	-	177.8	-	151	308.8	-	179.1	-	152.8	306	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI550K5-625AXSP08	-	244.8	186.5	210.2	407.4	-	244.7	187.6	210.5	402.7	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI550K5-525AXSP06	-	220.7	-	187.8	379.5	-	222.3	-	189.9	376.2	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI550K5-425AXSP06	-	198.8	147.3	168.9	346.7	-	200.7	150.2	170.7	344.1	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI750K5-625AXSP08	-	265.7	202.2	228.1	443.4	170.4	265.7	203.6	228.5	439	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI750K5-525AXSP06	-	239.2	-	203.8	412.6	-	241.3	-	206.1	410	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI750K5-425AXSP06	-	215.3	159.4	182.8	376.5	-	217.3	162.3	184.8	374	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI370C4-625AXSP08	-	226.8	173.1	194.9	376.3	-	226.3	173.9	194.9	371.5	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI370C4-525AXSP08	-	214.1	162.4	183.6	359.6	-	213.9	163.2	183.5	355.1	303	22.7	3"	242	15	3"	363	31.9	3"
EAW-VD15S2PI370C4-425AXSP06	-	184.8	-	157.1	321.1	-	186.2	-	158.7	318.6	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI550C4-625AXSP08	-	257.8	196.3	221.5	430	-	257.6	197.2	221.3	424.8	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI550C4-525AXSP06	-	231.4	-	197.1	398.7	-	233.2	-	199	395.7	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI550C4-425AXSP06	-	207.7	153.8	176.3	362.5	-	209.3	156.6	178.1	360.1	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI750C4-625AXSP06	-	265.6	-	226.4	452.9	-	267.6	-	228.9	449.5	484	20.1	3"	388	13.2	3"	581	24.1	4"
EAW-VD15S2PI750C4-525AXSP06	-	248.1	-	211.2	428.7	-	250.1	188.1	213.5	425.5	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI750C4-425AXSP06	-	222.8	164.6	189	389.8	-	224.6	167.7	191.1	387.3	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI370C5-625AXSP08	-	226.8	173.1	194.9	376.3	-	226.3	173.9	194.9	371.5	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI370C5-525AXSP08	-	214.1	162.4	183.6	359.6	-	213.9	163.2	183.5	355.1	303	22.7	3"	242	15	3"	363	31.9	3"
EAW-VD15S2PI370C5-425AXSP06	-	184.8	-	157.1	321.1	-	186.2	-	158.7	318.6	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI550C5-625AXSP08	-	257.8	196.3	221.5	430	-	257.6	197.2	221.3	424.8	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI550C5-525AXSP06	-	231.4	-	197.1	398.7	-	233.2	-	199	395.7	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI550C5-425AXSP06	-	207.7	153.8	176.3	362.5	-	209.3	156.6	178.1	360.1	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI750C5-625AXSP06	-	265.6	-	226.4	452.9	-	267.6	-	228.9	449.5	484	20.1	3"	388	13.2	3"	581	24.1	4"
EAW-VD15S2PI750C5-525AXSP06	-	248.1	-	211.2	428.7	-	250.1	188.1	213.5	425.5	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI750C5-425AXSP06	-	222.8	164.6	189	389.8	-	224.6	167.7	191.1	387.3	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI370K8-625AXSP08	-	217.2	-	186.6	359.6	-	216.7	-	186.7	355.1	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI370K8-525AXSP08	-	205.3	155.9	176.2	344.1	-	205.1	156.7	176.1	340.2	303	22.7	3"	242	15	3"	363	31.9	3"
EAW-VD15S2PI370K8-425AXSP06	-	177.8	-	151	308.8	-	179.1	-	152.8	306	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI550K8-625AXSP08	-	244.8	186.5	210.2	407.4	-	244.7	187.6	210.5	402.7	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI550K8-525AXSP06	-	220.7	-	187.8	379.5	-	222.3	-	189.9	376.2	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI550K8-425AXSP06	-	198.8	147.3	168.9	346.7	-	200.7	150.2	170.7	344.1	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S2PI750K8-625AXSP08	-	265.7	202.2	228.1	443.4	170.4	265.7	203.6	228.5	439	363	23.5	3"	291	15.5	3"	436	33	3"
EAW-VD15S2PI750K8-525AXSP06	-	239.2	-	203.8	412.6	-	241.3	-	206.1	410	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD15S2PI750K8-425AXSP06	-	215.3	159.4	182.8	376.5	-	217.3	162.3	184.8	374	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD15S3PI370K4-625AXSP06	-	328.5	252.2	283.1	541.3	-	327.4	252.6	282.2	533.8	484	27	3"	388	17.8	3"	581	33.9	4"
EAW-VD15S3PI370K4-525AXSP04	-	294	-	-	504.3	-	296.5	-	-	499.9	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI370K4-425AXSP04	-	268.3	-	228.1	466.4	-	270.7	-	230.7	462.8	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI550K4-625AXSP04	-	351.1	-	-	597.7	-	354	-	-	592.4	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI550K4-525AXSP04	-	330.5	-	281.7	569.2	-	333.5	-	284.5	564.3	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI550K4-425AXSP04	-	300.6	-	255.2	523.8	-	303.4	226.9	258.2	520.5	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI750K4-625AXSP04	-	381.1	-	-	650.4	-	384.5	-	-	645.6	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI750K4-525AXSP04	-	358.7	-	305.2	619	-	362	-	308.7	615	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI750K4-425AXSP04	-	325.6	240.9	276.3	568.9	-	328.7	245.7	279.6	565.1	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI370K5-625AXSP06	-	328.5	252.2	283.1	541.3	-	327.4	252.6	282.2	533.8	484	27	3"	388	17.8	3"	581	33.9	4"
EAW-VD15S3PI370K5-525AXSP04	-	294	-	-	504.3	-	296.5	-	-	499.9	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI370K5-425AXSP04	-	268.3	-	228.1	466.4	-	270.7	-	230.7	462.8	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI550K5-625AXSP04	-	351.1	-	-	597.7	-	354	-	-	592.4	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI550K5-525AXSP04	-	330.5	-	281.7	569.2	-	333.5	-	284.5	564.3	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI550K5-425AXSP04	-	300.6	-	255.2	523.8	-	303.4	226.9	258.2	520.5	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI750K5-625AXSP04	-	381.1	-	-	650.4	-	384.5	-	-	645.6	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI750K5-525AXSP04	-	358.7	-	305.2	619	-	362	-	308.7	615	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI750K5-425AXSP04	-	325.6	240.9	276.3	568.9	-	328.7	245.7	279.6	565.1	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI370C4-625AXSP06	-	343.5	263.1	295.5	566.3	-	342	263.5	294.9	559.1	484	27	3"	388	17.8	3"	581	33.9	4"
EAW-VD15S3PI370C4-525AXSP04	-	306.9	-	-	526.3	-	309.1	-	-	521.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI370C4-425AXSP04	-	279.4	-	237.2	485.7	-	281.4	-	240	481.8	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI550C4-625AXSP04	-	369.9	-	-	630.7	-	372.4	-	-	624.8	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI550C4-525AXSP04	-	346.6	-	295.1	598.1	-	349.7	-	298.5	593.5	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI550C4-425AXSP04	-	314.2	232.5	266.8	547.8	-	316.5	236.6	269.5	544	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI750C4-625AXSP04	-	396.2	-	338.1	676.9	-	399.2	-	341.9	671.8	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI750C4-525AXSP04	-	371.6	-	316.3	642.1	-	375.2	282.1	320.2	638.3	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI750C4-425AXSP04	-	336.5	248.9	285.7	589.1	-	339.8	254	289.2	586	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI370C5-625AXSP06	-	343.5	263.1	295.5	566.3	-	342	263.5	294.9	559.1	484	27	3"	388	17.8	3"	581	33.9	4"
EAW-VD15S3PI370C5-525AXSP04	-	306.9	-	-	526.3	-	309.1	-	-	521.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI370C5-425AXSP04	-	279.4	-	237.2	485.7	-	281.4	-	240	481.8	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI550C5-625AXSP04	-	369.9	-	-	630.7	-	372.4	-	-	624.8	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI550C5-525AXSP04	-	346.6	-	295.1	598.1	-	349.7	-	298.5	593.5	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI550C5-425AXSP04	-	314.2	232.5	266.8	547.8	-	316.5	236.6	269.5	544	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI750C5-625AXSP04	-	396.2	-	338.1	676.9	-	399.2	-	341.9	671.8	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI750C5-525AXSP04	-	371.6	-	316.3	642.1	-	375.2	282.1	320.2	638.3	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI750C5-425AXSP04	-	336.5	248.9	285.7	589.1	-	339.8	254	289.2	586	484	19.4	3"	388	12.8	3"	581	23.2	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PI370K8-625AXSP06	-	328.5	252.2	283.1	541.3	-	327.4	252.6	282.2	533.8	484	27	3"	388	17.8	3"	581	33.9	4"
EAW-VD15S3PI370K8-525AXSP04	-	294	-	-	504.3	-	296.5	-	-	499.9	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI370K8-425AXSP04	-	268.3	-	228.1	466.4	-	270.7	-	230.7	462.8	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI550K8-625AXSP04	-	351.1	-	-	597.7	-	354	-	-	592.4	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI550K8-525AXSP04	-	330.5	-	281.7	569.2	-	333.5	-	284.5	564.3	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI550K8-425AXSP04	-	300.6	-	255.2	523.8	-	303.4	226.9	258.2	520.5	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S3PI750K8-625AXSP04	-	381.1	-	-	650.4	-	384.5	-	-	645.6	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD15S3PI750K8-525AXSP04	-	358.7	-	305.2	619	-	362	-	308.7	615	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD15S3PI750K8-425AXSP04	-	325.6	240.9	276.3	568.9	-	328.7	245.7	279.6	565.1	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD15S4PI370K4-625AXSP04	-	431.2	-	370.7	716	-	430.4	-	370.6	706.2	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI370K4-525AXSP04	-	407.3	309.1	349.4	684	-	407	311.1	349.7	676.3	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI370K4-425AXSP04	229.10	372.4	280.5	318.4	633.8	234.2	372.4	282.4	319	627	484	24.1	3"	388	15.9	3"	581	29.7	4"
EAW-VD15S4PI550K4-625AXSP04	-	485.9	370.4	417.6	810	-	485.8	372.7	418.2	800.8	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI550K4-525AXSP04	284.60	457.8	346.6	392.4	772.5	290.6	458.2	348.9	392.9	764.6	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI550K4-425AXSP02	-	-	-	-	660.6	-	-	-	-	661	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI750K4-625AXSP04	-	527.2	400.9	452.5	881.7	337.8	528.1	403.8	454	873	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI750K4-525AXSP02	-	-	-	-	782.3	-	-	-	-	782.3	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI750K4-425AXSP02	-	-	-	-	716.2	-	-	-	-	716.6	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI370K5-625AXSP04	-	431.2	-	370.7	716	-	430.4	-	370.6	706.2	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI370K5-525AXSP04	-	407.3	309.1	349.4	684	-	407	311.1	349.7	676.3	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI370K5-425AXSP04	229.10	372.4	280.5	318.4	633.8	234.2	372.4	282.4	319	627	484	24.1	3"	388	15.9	3"	581	29.7	4"
EAW-VD15S4PI550K5-625AXSP04	-	485.9	370.4	417.6	810	-	485.8	372.7	418.2	800.8	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI550K5-525AXSP04	284.60	457.8	346.6	392.4	772.5	290.6	458.2	348.9	392.9	764.6	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI550K5-425AXSP02	-	-	-	-	660.6	-	-	-	-	661	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI750K5-625AXSP04	-	527.2	400.9	452.5	881.7	337.8	528.1	403.8	454	873	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI750K5-525AXSP02	-	-	-	-	782.3	-	-	-	-	782.3	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI750K5-425AXSP02	-	-	-	-	716.2	-	-	-	-	716.6	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI370C4-625AXSP04	-	450.7	343.3	387.3	749.1	-	449.9	345.4	387.3	739.7	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI370C4-525AXSP04	-	424.7	321.8	364	714.9	-	424.5	324	364.5	706	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI370C4-425AXSP02	-	-	-	-	612.5	-	-	-	-	611.8	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI550C4-625AXSP04	-	511.6	389.4	439.3	854.9	-	511.3	391.8	439.8	844.7	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI550C4-525AXSP02	-	-	-	-	756.4	-	-	-	-	755.3	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI550C4-425AXSP02	-	-	-	-	690.2	-	-	-	-	690.4	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI750C4-625AXSP04	343.30	548.4	416.5	470.4	917.8	350.7	548.4	419.4	471.2	908.5	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI750C4-525AXSP02	-	-	-	-	812.2	-	-	-	-	812.5	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI750C4-425AXSP02	-	-	-	-	741	-	-	-	-	742.7	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI370C5-625AXSP04	-	450.7	343.3	387.3	749.1	-	449.9	345.4	387.3	739.7	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI370C5-525AXSP04	-	424.7	321.8	364	714.9	-	424.5	324	364.5	706	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI370C5-425AXSP02	-	-	-	-	612.5	-	-	-	-	611.8	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI550C5-625AXSP04	-	511.6	389.4	439.3	854.9	-	511.3	391.8	439.8	844.7	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI550C5-525AXSP02	-	-	-	-	756.4	-	-	-	-	755.3	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI550C5-425AXSP02	-	-	-	-	690.2	-	-	-	-	690.4	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI750C5-625AXSP04	343.30	548.4	416.5	470.4	917.8	350.7	548.4	419.4	471.2	908.5	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI750C5-525AXSP02	-	-	-	-	812.2	-	-	-	-	812.5	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI750C5-425AXSP02	-	-	-	-	741	-	-	-	-	742.7	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI370K8-625AXSP04	-	431.2	-	370.7	716	-	430.4	-	370.6	706.2	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI370K8-525AXSP04	-	407.3	309.1	349.4	684	-	407	311.1	349.7	676.3	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI370K8-425AXSP04	229.10	372.4	280.5	318.4	633.8	234.2	372.4	282.4	319	627	484	24.1	3"	388	15.9	3"	581	29.7	4"
EAW-VD15S4PI550K8-625AXSP04	-	485.9	370.4	417.6	810	-	485.8	372.7	418.2	800.8	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI550K8-525AXSP04	284.60	457.8	346.6	392.4	772.5	290.6	458.2	348.9	392.9	764.6	606	22	4"	484	17.4	3"	727	30.9	4"
EAW-VD15S4PI550K8-425AXSP02	-	-	-	-	660.6	-	-	-	-	661	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S4PI750K8-625AXSP04	-	527.2	400.9	452.5	881.7	337.8	528.1	403.8	454	873	727	22.9	4"	581	15.1	4"	872	32.2	4"
EAW-VD15S4PI750K8-525AXSP02	-	-	-	-	782.3	-	-	-	-	782.3	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD15S4PI750K8-425AXSP02	-	-	-	-	716.2	-	-	-	-	716.6	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD15S5PI370K4-625AXSP02	-	-	-	-	857.8	-	-	-	-	852.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI370K4-525AXSP02	-	-	-	-	817.8	-	-	-	-	812.1	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI370K4-425AXSP02	-	-	-	-	753.9	-	-	-	-	749.5	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI550K4-625AXSP02	-	-	-	-	970.5	-	-	-	-	964.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI550K4-525AXSP02	-	-	-	-	921	-	-	-	-	916.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI550K4-425AXSP02	-	474.8	-	-	845.6	-	483.3	-	-	843.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI750K4-625AXSP02	-	-	-	-	1054.1	-	-	-	-	1050.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI750K4-525AXSP02	-	567.9	-	-	1002.1	-	577.4	-	-	997.5	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI750K4-425AXSP02	-	513.4	-	-	917.5	-	523.7	-	-	914.8	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI370K5-625AXSP02	-	-	-	-	857.8	-	-	-	-	852.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI370K5-525AXSP02	-	-	-	-	817.8	-	-	-	-	812.1	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI370K5-425AXSP02	-	-	-	-	753.9	-	-	-	-	749.5	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI550K5-625AXSP02	-	-	-	-	970.5	-	-	-	-	964.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI550K5-525AXSP02	-	-	-	-	921	-	-	-	-	916.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI550K5-425AXSP02	-	474.8	-	-	845.6	-	483.3	-	-	843.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI750K5-625AXSP02	-	-	-	-	1054.1	-	-	-	-	1050.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI750K5-525AXSP02	-	567.9	-	-	1002.1	-	577.4	-	-	997.5	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI750K5-425AXSP02	-	513.4	-	-	917.5	-	523.7	-	-	914.8	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI370C4-625AXSP02	-	-	-	-	897.1	-	-	-	-	891.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI370C4-525AXSP02	-	-	-	-	853.2	-	-	-	-	848.4	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI370C4-425AXSP02	-	-	-	-	783.6	-	448.8	-	-	780.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI550C4-625AXSP02	-	-	-	-	1023.7	-	-	-	-	1017	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI550C4-525AXSP02	-	-	-	-	967.3	-	-	-	-	962.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI550C4-425AXSP02	-	495.8	-	-	883.9	-	504.6	-	-	881	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI750C4-625AXSP02	-	-	-	-	1096.9	-	-	-	-	1093.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI750C4-525AXSP02	-	587.7	-	-	1039.2	-	599	-	-	1036.3	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI750C4-425AXSP02	-	531	-	448.1	949.6	-	541	-	458.1	946.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI370C5-625AXSP02	-	-	-	-	897.1	-	-	-	-	891.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI370C5-525AXSP02	-	-	-	-	853.2	-	-	-	-	848.4	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI370C5-425AXSP02	-	-	-	-	783.6	-	448.8	-	-	780.1	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI550C5-625AXSP02	-	-	-	-	1023.7	-	-	-	-	1017	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI550C5-525AXSP02	-	-	-	-	967.3	-	-	-	-	962.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI550C5-425AXSP02	-	495.8	-	-	883.9	-	504.6	-	-	881	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI750C5-625AXSP02	-	-	-	-	1096.9	-	-	-	-	1093.1	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI750C5-525AXSP02	-	587.7	-	-	1039.2	-	599	-	-	1036.3	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI750C5-425AXSP02	-	531	-	448.1	949.6	-	541	-	458.1	946.9	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI370K8-625AXSP02	-	-	-	-	857.8	-	-	-	-	852.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI370K8-525AXSP02	-	-	-	-	817.8	-	-	-	-	812.1	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI370K8-425AXSP02	-	-	-	-	753.9	-	-	-	-	749.5	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI550K8-625AXSP02	-	-	-	-	970.5	-	-	-	-	964.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI550K8-525AXSP02	-	-	-	-	921	-	-	-	-	916.9	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI550K8-425AXSP02	-	474.8	-	-	845.6	-	483.3	-	-	843.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD15S5PI750K8-625AXSP02	-	-	-	-	1054.1	-	-	-	-	1050.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD15S5PI750K8-525AXSP02	-	567.9	-	-	1002.1	-	577.4	-	-	997.5	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD15S5PI750K8-425AXSP02	-	513.4	-	-	917.5	-	523.7	-	-	914.8	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD9102ZA320P7-625AXSP16	-	-	-	-	161.9	-	-	-	-	161.7	242	15.4	3"	194	13.3	2"	291	21.7	3"
EAW-VD9102ZA320P7-525AXSP16	-	-	-	-	149.7	-	-	-	-	149.6	194	18.1	2"	155	11.9	2"	232	25.5	2"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9102ZA320P7-425AXSP16	-	74.8	-	-	137	-	76.8	-	-	137.1	157	16.8	2"	126	14.2	1-1/2"	189	23.7	2"
EAW-VD9104ZA320P7-625AXSP12	-	197.1	-	168	336.9	-	198.6	-	169.9	334.4	327	19.7	3"	262	13	3"	392	27.7	3"
EAW-VD9104ZA320P7-525AXSP12	-	182	135.5	154.8	315.2	-	183.6	138	156.6	313.4	266	19.1	3"	213	16.3	2"	320	26.7	3"
EAW-VD9104ZA320P7-425AXSP12	-	166.2	123	141.1	290.8	101.8	167.8	125.1	142.7	289.3	218	22.5	2"	174	14.8	2"	262	26.1	3"
EAW-VD9106ZA320P7-625AXSP08	-	293.2	-	250.1	501.7	-	295.5	-	252.7	497.9	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD9106ZA320P7-525AXSP08	-	272.1	202.5	231.5	471.6	-	274.5	206.3	234.1	468.8	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD9106ZA320P7-425AXSP08	-	248.4	183.8	210.9	435.5	152	250.9	187.4	213.2	432.7	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD9108ZA320P7-625AXSP06	-	392	-	334.5	671.4	-	395.1	-	337.9	666.3	654	18.4	4"	523	12.1	4"	785	25.9	4"
EAW-VD9108ZA320P7-525AXSP06	-	366.2	272.4	311.7	633.9	-	369.3	277.4	315.2	630.1	545	17.6	4"	436	14.1	3"	654	24.7	4"
EAW-VD9108ZA320P7-425AXSP06	-	330	244	280.1	578.9	201.9	333.4	248.8	283.3	575.2	436	19.4	3"	349	12.8	3"	523	23.8	4"
EAW-VD9110ZA320P7-625AXSP04	-	471.6	-	-	822.7	-	479.3	-	-	819.8	981	14.3	(2) 4"	785	12.3	4"	1177	20.1	(2) 4"
EAW-VD9110ZA320P7-525AXSP04	-	438.8	-	-	774.2	-	445.9	-	378.4	771	812	16.9	4"	649	11.1	4"	974	19.4	(2) 4"
EAW-VD9110ZA320P7-425AXSP04	-	396.5	-	334.9	708.2	-	403.3	-	341.2	705	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD9112ZA320P7-625AXSP04	-	584.7	-	498.7	1002.2	-	589.5	-	503.9	994.6	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD9112ZA320P7-525AXSP04	-	544.3	404.4	463	943.2	-	549.1	411.9	468.3	937.6	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD9112ZA320P7-425AXSP04	-	491.5	363.4	417	863.1	-	496.7	370.4	422.6	857.7	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD9114ZA320P7-625AXSP04	-	697.4	525.6	596.6	1180.7	-	699.8	531.5	599.8	1171.7	981	18.9	(2) 4"	785	15.4	4"	1177	26.6	(2) 4"
EAW-VD9114ZA320P7-525AXSP04	394.40	648.7	486.7	553.6	1112.3	405.8	652.1	492.7	557.7	1104.1	812	21.5	4"	649	14.2	4"	974	25.9	(2) 4"
EAW-VD9114ZA320P7-425AXSP02	-	-	-	-	932.8	-	-	-	-	935.9	1308	11.3	(2) 4"	1046	7.5	(2) 4"	1570	16	(2) 4"
EAW-VD9116ZA320P7-625AXSP02	-	-	-	-	1270.1	-	-	-	-	1269.7	1962	12.5	(3) 4"	1570	10.3	(2) 4"	2354	17.6	(3) 4"
EAW-VD9116ZA320P7-525AXSP02	-	-	-	-	1194.4	-	-	-	-	1195.2	1635	14	(2) 4"	1308	9.2	(2) 4"	1962	16.4	(3) 4"
EAW-VD9116ZA320P7-425AXSP02	-	-	-	-	1085.4	-	605.6	-	-	1086.8	1308	12.5	(2) 4"	1046	8.2	(2) 4"	1570	17.6	(2) 4"
EAW-VD9118ZA320P7-625AXSP02	-	-	-	-	1447.4	-	-	-	-	1442.9	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD9118ZA320P7-525AXSP02	-	759.5	-	-	1362.9	-	776.7	-	-	1359.6	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD9118ZA320P7-425AXSP02	-	682.3	-	-	1237	-	697.9	-	-	1236.2	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD9120ZA320P7-625AXSP02	-	927	-	-	1624.8	-	942.6	-	-	1617.3	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD9120ZA320P7-525AXSP02	-	863.5	-	-	1529.3	-	879.5	-	-	1525.3	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD9120ZA320P7-425AXSP02	-	775.6	-	654.2	1389.9	-	789.6	-	668.1	1386.4	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD9102ZJ320P7-625AXSP16	-	-	-	-	171.7	-	-	-	-	170.8	242	16.5	3"	194	14	2"	291	23.1	3"
EAW-VD9102ZJ320P7-525AXSP16	-	-	-	-	158.8	-	90.8	-	-	158.2	194	19.2	2"	155	12.6	2"	232	27	2"
EAW-VD9102ZJ320P7-425AXSP16	-	80.6	-	-	145.4	-	82.3	-	-	145.1	157	17.9	2"	126	14.9	1-1/2"	189	25.1	2"
EAW-VD9104ZJ320P7-625AXSP12	-	210	158.4	179.6	355.7	-	210.9	160.3	180.8	352	327	21.3	3"	262	14.1	3"	392	29.9	3"
EAW-VD9104ZJ320P7-525AXSP12	-	194.1	145.4	165.6	333	-	195	147.2	166.8	330	266	20.6	3"	213	17.4	2"	320	28.9	3"
EAW-VD9104ZJ320P7-425AXSP08	-	164.1	-	-	295.8	-	167.6	-	-	295	327	14.9	3"	262	9.8	3"	392	20.9	3"
EAW-VD9106ZJ320P7-625AXSP08	-	312.5	235.5	267.2	529.7	-	313.9	238.4	268.9	524.9	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD9106ZJ320P7-525AXSP08	-	290.3	217.4	247.6	498.1	-	291.7	220.1	249.4	493.8	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD9106ZJ320P7-425AXSP06	-	251.5	-	212.6	447.8	-	255.3	-	216.4	445.8	436	17.1	3"	349	11.3	3"	523	20.5	4"
EAW-VD9108ZJ320P7-625AXSP06	-	417.8	314.9	357.7	708.8	-	419.7	318.8	359.6	701.5	654	20	4"	523	13.2	4"	785	28.1	4"
EAW-VD9108ZJ320P7-525AXSP06	-	390.5	292.3	333.2	669.5	-	392.3	296.3	335.6	663.5	545	19.2	4"	436	15.1	3"	654	26.9	4"
EAW-VD9108ZJ320P7-425AXSP06	210.60	352	261.9	299.7	610.6	217.4	353.7	265.7	301.8	605.8	436	21	3"	349	13.8	3"	523	25.9	4"
EAW-VD9110ZJ320P7-625AXSP04	-	505.4	-	-	871.1	-	510.9	-	-	864.4	981	15.6	(2) 4"	785	13.2	4"	1177	21.9	(2) 4"
EAW-VD9110ZJ320P7-525AXSP04	-	470	-	398.8	819.3	-	474.9	-	404.7	813.3	812	18.2	4"	649	12	4"	974	21.2	(2) 4"
EAW-VD9110ZJ320P7-425AXSP04	-	424.4	312.5	359.7	748.5	-	429.8	319.3	364.7	744	654	16.8	4"	523	11	4"	785	23.5	4"
EAW-VD9112ZJ320P7-625AXSP04	-	624.2	469.6	533.5	1058.1	-	626.2	475.5	537.1	1048.5	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD9112ZJ320P7-525AXSP04	-	580.5	434.1	495.1	996.3	-	583.4	440.2	497.9	987.5	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD9112ZJ320P7-425AXSP04	313.30	524.5	390.5	446.3	911.8	323.5	527.9	395.6	449.5	904.7	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD9114ZJ320P7-625AXSP04	462.70	742	562.7	635.9	1246.4	473.1	742.1	566.9	637.1	1232	981	20.8	(2) 4"	785	16.6	4"	1177	29.1	(2) 4"
EAW-VD9114ZJ320P7-525AXSP02	-	-	-	-	1093.2	-	-	-	-	1092.2	1635	13.7	(2) 4"	1308	9	(2) 4"	1962	16.1	(3) 4"
EAW-VD9114ZJ320P7-425AXSP02	-	-	-	-	991	-	-	-	-	992.4	1308	12.2	(2) 4"	1046	8.1	(2) 4"	1570	17.2	(2) 4"
EAW-VD9116ZJ320P7-625AXSP02	-	-	-	-	1347.7	-	-	-	-	1343.1	1962	13.5	(3) 4"	1570	11	(2) 4"	2354	19	(3) 4"
EAW-VD9116ZJ320P7-525AXSP02	-	-	-	-	1268.7	-	-	-	-	1265.4	1635	15	(2) 4"	1308	9.9	(2) 4"	1962	17.9	(3) 4"
EAW-VD9116ZJ320P7-425AXSP02	-	633.8	-	-	1152.5	-	649.4	-	-	1150	1308	13.5	(2) 4"	1046	8.9	(2) 4"	1570	19	(2) 4"
EAW-VD9118ZJ320P7-625AXSP02	-	-	-	-	1533.4	-	-	-	-	1526	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD9118ZJ320P7-525AXSP02	-	816.2	-	-	1443.1	-	830.8	-	-	1437	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD9118ZJ320P7-425AXSP02	-	733.1	-	618.1	1312.8	-	746.2	-	631.5	1307.6	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD9102PA320P7-625AXSP16	-	-	-	-	138.8	-	-	-	-	139.1	182	17.5	2"	145	11.5	2"	218	24.6	2"
EAW-VD9102PA320P7-525AXSP16	-	70.7	-	-	128.7	-	72.9	-	-	129.2	145	16.3	2"	116	13.2	1-1/2"	174	23	2"
EAW-VD9102PA320P7-425AXSP16	-	65.4	-	-	120.4	-	67.4	-	56.7	120.6	121	18.3	1-1/2"	97	12.1	1-1/2"	145	22.1	2"
EAW-VD9104PA320P7-625AXSP12	-	167.3	124.8	142.6	287.6	-	169.2	127.6	144.5	286.5	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD9104PA320P7-525AXSP12	90.90	153.5	114	130.5	267.4	94.8	155.2	116.4	132.2	266.6	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD9104PA320P7-425AXSP08	-	130.1	-	-	239.5	-	134.1	-	112.7	240.4	242	12.8	3"	194	11.4	2"	291	18	3"
EAW-VD9106PA320P7-625AXSP08	-	250.3	186.7	213.2	430.8	-	253.1	190.7	216.1	429.2	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD9106PA320P7-525AXSP08	-	234.9	174.4	199.5	408.6	145.2	237.7	178	202.4	407.3	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD9106PA320P7-425AXSP06	-	197.1	-	165.7	357.5	-	201.9	147.7	170.3	358.3	315	14.1	3"	252	9.3	3"	378	19.8	3"
EAW-VD9108PA320P7-625AXSP06	-	332.7	248.1	283.4	572.9	-	336.5	253.5	287.3	570.8	484	20.1	3"	388	13.2	3"	581	24.1	4"
EAW-VD9108PA320P7-525AXSP06	-	310.6	230.5	263.7	541	191.8	314	235.2	267.7	538.5	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD9108PA320P7-425AXSP04	-	257	-	-	474.2	-	265.1	-	-	476.1	484	14.8	3"	388	9.7	3"	581	16.7	4"
EAW-VD9110PA320P7-625AXSP04	-	400.2	-	339.4	702.4	-	408.2	-	346.7	700.9	727	16	4"	581	10.5	4"	872	22.5	4"
EAW-VD9110PA320P7-525AXSP04	-	375	-	317	665.7	-	382.5	283.6	324.4	664.7	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD9110PA320P7-425AXSP04	-	339.1	246.4	285.8	608	-	345.7	254.6	292.1	608	484	17.1	3"	388	11.3	3"	581	20	4"
EAW-VD9112PA320P7-625AXSP04	-	496.2	369.7	422.5	855	-	501.9	377.9	428.4	851.9	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD9112PA320P7-525AXSP04	-	465.2	345.1	395.6	811.5	287.1	470.9	352.2	400.8	807.8	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD9112PA320P7-425AXSP02	-	-	-	-	667.7	-	-	-	-	676.2	969	8.9	(2) 4"	775	8.6	4"	1163	12.6	(2) 4"
EAW-VD9114PA320P7-625AXSP04	362.00	591.6	444.8	505.3	1009	373.5	596.4	451.3	510.4	1002.7	727	20.6	4"	581	13.6	4"	872	29	4"
EAW-VD9114PA320P7-525AXSP02	-	-	-	-	878.1	-	-	-	-	884.5	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.3	(2) 4"
EAW-VD9114PA320P7-425AXSP02	-	-	-	-	798.8	-	-	-	-	805.5	969	10.1	(2) 4"	775	9.4	4"	1163	14.2	(2) 4"
EAW-VD9116PA320P7-625AXSP02	-	-	-	-	1081.2	-	-	-	-	1085.5	1453	13	(2) 4"	1163	8.6	(2) 4"	1744	18.3	(2) 4"
EAW-VD9116PA320P7-525AXSP02	-	-	-	-	1022	-	575.4	-	-	1025.9	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD9116PA320P7-425AXSP02	-	501.8	-	-	930.7	-	518.5	-	-	934.9	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD9118PA320P7-625AXSP02	-	691	-	-	1232.9	-	709.2	-	-	1234.1	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD9118PA320P7-525AXSP02	-	646.5	-	-	1165.3	-	662.9	-	-	1167.7	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD9118PA320P7-425AXSP02	-	582.4	-	488.8	1061.6	-	597.6	-	503.4	1064.2	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD9120PA320P7-625AXSP02	-	786	-	-	1384.6	-	802.2	-	681.6	1383.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD9120PA320P7-525AXSP02	-	734.8	-	621.2	1308.3	-	750.2	-	635.3	1308.7	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD9120PA320P7-425AXSP02	-	662.5	480.6	558.3	1193.7	-	677	497.1	571.8	1194.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD9102PJ320P7-625AXSP16	-	84.2	-	-	149	-	86.1	-	-	148.9	182	18.5	2"	145	12.2	2"	218	26	2"
EAW-VD9102PJ320P7-525AXSP16	-	77.1	-	-	138.1	-	78.9	-	-	138.2	145	17.4	2"	116	13.9	1-1/2"	174	24.4	2"
EAW-VD9102PJ320P7-425AXSP16	-	71.2	-	59.9	128.9	-	72.9	-	61.5	128.9	121	19.4	1-1/2"	97	12.7	1-1/2"	145	23.5	2"
EAW-VD9104PJ320P7-625AXSP12	-	180.6	135.9	154.4	307.7	113.8	181.9	137.8	155.7	305.7	242	20.3	3"	194	16.3	2"	291	28.5	3"
EAW-VD9104PJ320P7-525AXSP08	-	156.8	-	-	281.1	-	160.6	-	-	281.1	303	14.5	3"	242	9.6	3"	363	20.4	3"
EAW-VD9104PJ320P7-425AXSP08	-	141.6	-	119.1	256.5	-	144.9	-	122.4	256.5	242	13.9	3"	194	12.1	2"	291	19.5	3"
EAW-VD9106PJ320P7-625AXSP08	-	270.1	203.1	230.9	460.3	170.1	272.1	206.1	232.8	457.4	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD9106PJ320P7-525AXSP06	-	239.2	-	202.5	423.4	-	243.5	-	206.8	422.2	400	16.4	3"	320	10.8	3"	480	23.1	3"
EAW-VD9106PJ320P7-425AXSP06	-	213.6	155.8	180.5	382.9	-	217.8	160.6	184.2	382.3	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD9108PJ320P7-625AXSP06	-	359.1	270	307	612.3	226.1	361.9	273.9	309.5	608.3	484	21.6	3"	388	14.2	3"	581	26.3	4"
EAW-VD9108PJ320P7-525AXSP04	-	310.5	-	-	557.4	-	318	-	-	557.4	606	13.7	4"	484	12	3"	727	19.3	4"
EAW-VD9108PJ320P7-425AXSP04	-	279.9	-	235.4	508.9	-	286.7	-	242	509	484	15.8	3"	388	10.4	3"	581	18.2	4"
EAW-VD9110PJ320P7-625AXSP04	-	434.3	-	369.3	751.9	-	440	-	375.1	749.1	727	17.3	4"	581	11.4	4"	872	24.3	4"
EAW-VD9110PJ320P7-525AXSP04	-	406.6	300.2	344.7	711.7	-	412.3	307.7	350.6	709.5	606	16.3	4"	484	13.7	3"	727	22.9	4"
EAW-VD9110PJ320P7-425AXSP04	-	366.4	269.2	310.2	649.7	-	371.8	275.9	315.6	648.5	484	18.4	3"	388	12.1	3"	581	21.8	4"
EAW-VD9112PJ320P7-625AXSP04	-	535.6	402.4	457.7	914.9	337	539.8	408.4	461.6	909.1	727	19.8	4"	581	13.1	4"	872	27.9	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9112PJ320P7-525AXSP02	-	-	-	-	792.8	-	-	-	-	798.5	1211	10.5	(2) 4"	969	6.9	(2) 4"	1453	14.8	(2) 4"
EAW-VD9112PJ320P7-425AXSP02	-	-	-	-	720.6	-	-	-	-	725.4	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD9114PJ320P7-625AXSP02	-	-	-	-	1001.5	-	-	-	-	1004	1453	12.8	(2) 4"	1163	8.4	(2) 4"	1744	18	(2) 4"
EAW-VD9114PJ320P7-525AXSP02	-	-	-	-	944.5	-	-	-	-	948.1	1211	11.8	(2) 4"	969	7.8	(2) 4"	1453	16.6	(2) 4"
EAW-VD9114PJ320P7-425AXSP02	-	461.6	-	-	859.7	-	478.1	-	-	862.1	969	11	(2) 4"	775	10	4"	1163	15.5	(2) 4"
EAW-VD9116PJ320P7-625AXSP02	-	-	-	-	1163	-	-	-	-	1162.4	1453	14.1	(2) 4"	1163	9.2	(2) 4"	1744	19.8	(2) 4"
EAW-VD9116PJ320P7-525AXSP02	-	608.3	-	-	1097.1	-	623.6	-	-	1097.6	1211	13.1	(2) 4"	969	8.6	(2) 4"	1453	18.4	(2) 4"
EAW-VD9116PJ320P7-425AXSP02	-	547.4	-	459.2	997.6	-	561.5	-	473.3	999.9	969	12.3	(2) 4"	775	10.8	4"	1163	17.3	(2) 4"
EAW-VD9118PJ320P7-625AXSP02	-	752.1	-	-	1322.2	-	767.4	-	-	1321.3	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD9118PJ320P7-525AXSP02	-	702.2	-	593.5	1248.6	-	716.7	-	607.8	1247.1	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD9118PJ320P7-425AXSP02	-	632.2	459	532.9	1137.4	-	645	474.6	545.1	1136	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD91S1MA320P7-625AXSP16	-	-	-	-	79.8	-	-	-	-	79.7	109	18.2	1-1/2"	87	12	1-1/2"	131	25.6	1-1/2"
EAW-VD91S1MA320P7-525AXSP16	-	-	-	-	74.9	-	-	-	-	74.9	97	16.7	1-1/2"	78	11	1-1/2"	116	23.4	1-1/2"
EAW-VD91S1MA320P7-425AXSP16	-	37.7	-	-	68.5	-	38.6	-	-	68.5	73	16.5	1-1/2"	58	10.9	1-1/2"	87	23.2	1-1/2"
EAW-VD91S2MA320P7-625AXSP12	-	96.8	-	82.4	165.5	-	97.6	73.7	83.3	164.3	157	19.9	2"	126	15.7	1-1/2"	189	28	2"
EAW-VD91S2MA320P7-525AXSP12	-	91.5	68.4	78.1	157.6	57.1	92.2	69.5	78.7	156.5	121	22.9	1-1/2"	97	15.1	1-1/2"	145	28.7	2"
EAW-VD91S2MA320P7-425AXSP08	-	74.7	-	-	137.1	-	76.9	-	-	137.2	157	14	2"	126	11.8	1-1/2"	189	19.7	2"
EAW-VD91S3MA320P7-625AXSP08	-	142.9	106.8	121.8	244.9	-	144.2	108.8	123.2	243.5	230	21.2	2"	184	13.9	2"	276	24.3	3"
EAW-VD91S3MA320P7-525AXSP08	-	134.2	99.8	114.1	232.6	-	135.4	101.7	115.5	231	194	19.8	2"	155	13	2"	232	27.8	2"
EAW-VD91S3MA320P7-425AXSP08	-	122	90.2	103.5	213.8	74.7	123.1	92	104.7	212.5	157	18.6	2"	126	14.9	1-1/2"	189	26.2	2"
EAW-VD91S4MA320P7-625AXSP06	-	192.4	-	163.9	329.4	-	194.1	146.4	165.9	327.4	315	17.5	3"	252	11.6	3"	378	24.6	3"
EAW-VD91S4MA320P7-525AXSP06	-	176.9	131.4	150.4	307.2	-	178.6	134	152.2	305.1	254	16.9	3"	204	14.2	2"	305	23.7	3"
EAW-VD91S4MA320P7-425AXSP06	-	160.3	118.3	135.9	281.2	97.9	161.9	120.7	137.6	280	206	19.6	2"	165	12.9	2"	247	23.2	3"
EAW-VD91S5MA320P7-625AXSP04	-	231.5	-	-	404.1	-	235.4	-	-	402.3	472	16.7	3"	378	11	3"	567	19.8	4"
EAW-VD91S5MA320P7-525AXSP04	-	214.6	-	181.3	378.7	-	218.2	-	185	377.8	388	15.5	3"	310	10.2	3"	465	21.7	3"
EAW-VD91S5MA320P7-425AXSP04	-	194.7	-	164.3	347.6	-	198.1	146.3	167.8	346.8	315	14.6	3"	252	9.6	3"	378	20.5	3"
EAW-VD91S6MA320P7-625AXSP04	-	287.1	-	244.7	492.3	-	289.5	-	247.4	488.8	472	19.1	3"	378	12.5	3"	567	23	4"
EAW-VD91S6MA320P7-525AXSP04	-	265.8	197.5	225.9	462	-	268.4	201.4	228.7	458.9	388	17.8	3"	310	11.7	3"	465	25	3"
EAW-VD91S6MA320P7-425AXSP04	-	241.4	178.4	205	424.4	147.6	244.1	181.8	207.5	421.9	315	16.9	3"	252	11.1	3"	378	23.7	3"
EAW-VD9102ZA247I6-625AXSP16	-	-	-	-	142.4	-	-	-	-	142.4	242	15.4	3"	194	13.3	2"	291	21.7	3"
EAW-VD9102ZA247I6-525AXSP16	-	-	-	-	133	-	-	-	-	132.9	194	18.1	2"	155	11.9	2"	232	25.5	2"
EAW-VD9102ZA247I6-425AXSP16	-	-	-	-	122.8	-	-	-	-	122.9	157	16.8	2"	126	14.2	1-1/2"	189	23.7	2"
EAW-VD9104ZA247I6-625AXSP12	-	174.1	-	-	296.2	-	175.5	-	-	294	327	19.7	3"	262	13	3"	392	27.7	3"
EAW-VD9104ZA247I6-525AXSP12	-	162.2	-	138.2	279.6	-	163.5	-	139.7	277.9	266	19.1	3"	213	16.3	2"	320	26.7	3"
EAW-VD9104ZA247I6-425AXSP12	-	149.3	110.6	126.7	260.4	-	150.7	112.8	128.3	258.8	218	22.5	2"	174	14.8	2"	262	26.1	3"
EAW-VD9106ZA247I6-625AXSP08	-	259.1	-	-	441.6	-	261.2	-	-	438.5	484	20.9	3"	388	13.8	3"	581	25.1	4"
EAW-VD9106ZA247I6-525AXSP08	-	242.6	-	206.7	418.8	-	244.9	-	208.8	415.8	400	19.5	3"	320	12.8	3"	480	27.4	3"
EAW-VD9106ZA247I6-425AXSP08	-	223.2	165.2	189.4	389.5	-	225.3	168.6	191.7	387.1	327	18.5	3"	262	12.2	3"	392	25.9	3"
EAW-VD9108ZA247I6-625AXSP08	224.80	358.5	272.6	307.7	598.6	229.7	358.7	274.6	308.3	592.9	484	25.5	3"	388	16.8	3"	581	31.6	4"
EAW-VD9108ZA247I6-525AXSP06	-	326.3	-	277.7	562.8	-	328.9	-	281	558.7	545	17.6	4"	436	14.1	3"	654	24.7	4"
EAW-VD9108ZA247I6-425AXSP06	-	296.6	219.5	252.1	517.8	-	299.4	223.9	254.8	515.3	436	19.4	3"	349	12.8	3"	523	23.8	4"
EAW-VD9110ZA247I6-625AXSP06	-	445.8	338.3	382.5	748.3	-	447.2	341.4	383.9	741.1	654	21.9	4"	523	14.5	4"	785	30.8	4"
EAW-VD9110ZA247I6-525AXSP04	-	391.1	-	-	687	-	397.7	-	-	684.1	812	16.9	4"	649	11.1	4"	974	19.4	(2) 4"
EAW-VD9110ZA247I6-425AXSP04	-	356.3	-	-	634	-	362.7	-	307.4	632.2	654	15.5	4"	523	10.2	4"	785	21.7	4"
EAW-VD9112ZA247I6-625AXSP04	-	516.8	-	-	882.1	-	521.7	-	-	875.9	981	16.6	(2) 4"	785	13.8	4"	1177	23.3	(2) 4"
EAW-VD9112ZA247I6-525AXSP04	-	484.5	-	412.7	836.5	-	489.2	-	417.7	831.6	812	19.2	4"	649	12.6	4"	974	22.7	(2) 4"
EAW-VD9112ZA247I6-425AXSP04	-	441.8	327.3	375.4	772.2	-	446.2	333.4	380.1	768.6	654	17.8	4"	523	11.7	4"	785	25	4"
EAW-VD9114ZA247I6-625AXSP04	-	616	465.5	527.4	1039	-	618.9	471.2	530.9	1030.4	981	18.9	(2) 4"	785	15.4	4"	1177	26.6	(2) 4"
EAW-VD9114ZA247I6-525AXSP04	-	577.8	434.2	493.7	987.4	-	580.5	439.9	497	978.9	812	21.5	4"	649	14.2	4"	974	25.9	(2) 4"
EAW-VD9114ZA247I6-425AXSP04	317.90	527.7	393.7	449.1	911.5	327.5	530.8	399	452.8	904.4	654	20.1	4"	523	13.3	4"	785	28.2	4"
EAW-VD9116ZA247I6-625AXSP04	-	715.1	543.7	613.7	1195.9	458.2	716.4	547.7	615.9	1184.4	981	21.3	(2) 4"	785	16.9	4"	1177	29.8	(2) 4"
EAW-VD9116ZA247I6-525AXSP02	-	-	-	-	1061.3	-	-	-	-	1061.8	1635	14	(2) 4"	1308	9.2	(2) 4"	1962	16.4	(3) 4"
EAW-VD9116ZA247I6-425AXSP02	-	-	-	-	972	-	-	-	-	974.5	1308	12.5	(2) 4"	1046	8.2	(2) 4"	1570	17.6	(2) 4"
EAW-VD9118ZA247I6-625AXSP02	-	-	-	-	1274.1	-	-	-	-	1272.1	1962	13.7	(3) 4"	1570	11.1	(2) 4"	2354	19.2	(3) 4"
EAW-VD9118ZA247I6-525AXSP02	-	-	-	-	1210.4	-	-	-	-	1207.3	1635	15.1	(2) 4"	1308	10	(2) 4"	1962	18.1	(3) 4"
EAW-VD9118ZA247I6-425AXSP02	-	613.4	-	-	1108.9	-	627.7	-	-	1108	1308	13.7	(2) 4"	1046	9	(2) 4"	1570	19.2	(2) 4"
EAW-VD9120ZA247I6-625AXSP02	-	-	-	-	1429.7	-	-	-	-	1425.5	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD9120ZA247I6-525AXSP02	-	770.2	-	-	1359.5	-	783.6	-	-	1353.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD9120ZA247I6-425AXSP02	-	697.7	-	-	1247.2	-	710.9	-	-	1244	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD9102ZJ247I6-625AXSP16	-	-	-	-	151.2	-	-	-	-	150.5	242	16.5	3"	194	14	2"	291	23.1	3"
EAW-VD9102ZJ247I6-525AXSP16	-	-	-	-	141.2	-	-	-	-	140.6	194	19.2	2"	155	12.6	2"	232	27	2"
EAW-VD9102ZJ247I6-425AXSP16	-	-	-	-	130.4	-	74.2	-	-	130.1	157	17.9	2"	126	14.9	1-1/2"	189	25.1	2"
EAW-VD9104ZJ247I6-625AXSP12	-	185.7	-	159.2	313	-	186.4	-	160.1	309.9	327	21.3	3"	262	14.1	3"	392	29.9	3"
EAW-VD9104ZJ247I6-525AXSP12	-	173	129.9	147.8	295.5	-	173.9	131.6	148.8	292.7	266	20.6	3"	213	17.4	2"	320	28.9	3"
EAW-VD9104ZJ247I6-425AXSP12	-	159.2	119	135.8	275.2	-	160.1	120.5	136.6	272.6	218	24.1	2"	174	15.9	2"	262	28.2	3"
EAW-VD9106ZJ247I6-625AXSP08	-	276.7	-	236.8	466.8	-	277.5	-	238.3	462.1	484	22.5	3"	388	14.8	3"	581	27.2	4"
EAW-VD9106ZJ247I6-525AXSP08	-	258.8	194.2	221	442.2	-	260.1	196.7	222.5	438.5	400	21	3"	320	13.9	3"	480	29.5	3"
EAW-VD9106ZJ247I6-425AXSP08	-	238	177.8	202.9	411.7	-	239.3	180.1	204.2	408.4	327	20	3"	262	13.2	3"	392	28.1	3"
EAW-VD9108ZJ247I6-625AXSP06	-	369.9	-	316.6	623.8	-	371.5	-	318.5	617.6	654	20	4"	523	13.2	4"	785	28.1	4"
EAW-VD9108ZJ247I6-525AXSP06	-	348	261.4	297.3	594.1	-	349.6	264.8	299.3	589	545	19.2	4"	436	15.1	3"	654	26.9	4"
EAW-VD9108ZJ247I6-425AXSP06	-	316.9	236.2	269.6	547.4	-	318.1	239.3	271.8	543	436	21	3"	349	13.8	3"	523	25.9	4"
EAW-VD9110ZJ247I6-625AXSP06	-	474.4	361.6	407.8	788.9	305.2	473.7	363.5	407.8	780	654	23.8	4"	523	15.7	4"	785	33.5	4"
EAW-VD9110ZJ247I6-525AXSP04	-	418.9	-	-	727.5	-	423.8	-	-	722.5	812	18.2	4"	649	12	4"	974	21.2	(2) 4"
EAW-VD9110ZJ247I6-425AXSP04	-	382	-	323.6	671.6	-	386.4	-	328.3	667.4	654	16.8	4"	523	11	4"	785	23.5	4"
EAW-VD9112ZJ247I6-625AXSP04	-	552	-	472.3	932.5	-	554.4	-	475.2	923.2	981	18.2	(2) 4"	785	14.9	4"	1177	25.5	(2) 4"
EAW-VD9112ZJ247I6-525AXSP04	-	517.6	387.7	441.3	884.3	-	520.1	393.5	445	876.9	812	20.7	4"	649	13.7	4"	974	24.8	(2) 4"
EAW-VD9112ZJ247I6-425AXSP04	-	472.2	351.7	401.7	816.4	-	474.9	356.5	404.9	810	654	19.3	4"	523	12.7	4"	785	27.2	4"
EAW-VD9114ZJ247I6-625AXSP04	-	655.8	498.5	563.2	1096.8	-	656.6	502.6	564.1	1084.5	981	20.8	(2) 4"	785	16.6	4"	1177	29.1	(2) 4"
EAW-VD9114ZJ247I6-525AXSP04	380.60	615.1	464.7	526.7	1040.9	389.8	616.1	469	528.4	1030.8	812	23.3	4"	649	15.4	4"	974	28.4	(2) 4"
EAW-VD9114ZJ247I6-425AXSP02	-	-	-	-	889.8	-	-	-	-	890.6	1308	12.2	(2) 4"	1046	8.1	(2) 4"	1570	17.2	(2) 4"
EAW-VD9116ZJ247I6-625AXSP02	-	-	-	-	1189.3	-	-	-	-	1185.3	1962	13.5	(3) 4"	1570	11	(2) 4"	2354	19	(3) 4"
EAW-VD9116ZJ247I6-525AXSP02	-	-	-	-	1128	-	-	-	-	1125.2	1635	15	(2) 4"	1308	9.9	(2) 4"	1962	17.9	(3) 4"
EAW-VD9116ZJ247I6-425AXSP02	-	-	-	-	1034.1	-	-	-	-	1031.4	1308	13.5	(2) 4"	1046	8.9	(2) 4"	1570	19	(2) 4"
EAW-VD9118ZJ247I6-625AXSP02	-	-	-	-	1352.8	-	-	-	-	1344.7	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.9	(3) 4"
EAW-VD9118ZJ247I6-525AXSP02	-	-	-	-	1282.5	-	-	-	-	1277.4	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.7	(3) 4"
EAW-VD9118ZJ247I6-425AXSP02	-	659.9	-	-	1177.4	-	671.9	-	-	1172.3	1308	14.8	(2) 4"	1046	9.8	(2) 4"	1570	20.9	(2) 4"
EAW-VD9102PA247I6-625AXSP16	-	-	-	-	121.5	-	-	-	-	121.7	182	17.5	2"	145	11.5	2"	218	24.6	2"
EAW-VD9102PA247I6-525AXSP16	-	-	-	-	114	-	-	-	-	114.4	145	16.3	2"	116	13.2	1-1/2"	174	23	2"
EAW-VD9102PA247I6-425AXSP16	-	58.6	-	-	107.4	-	60.5	-	-	107.8	121	18.3	1-1/2"	97	12.1	1-1/2"	145	22.1	2"
EAW-VD9104PA247I6-625AXSP12	-	147.1	-	125.5	251.6	-	148.7	112.5	127.2	250.8	242	18.8	3"	194	15.3	2"	291	26.3	3"
EAW-VD9104PA247I6-525AXSP12	-	136.4	101.3	115.9	236.5	-	138	103.5	117.6	235.8	194	21.3	2"	155	14	2"	232	29.9	2"
EAW-VD9104PA247I6-425AXSP08	-	116.6	-	-	213.8	-	120.3	-	-	214.6	242	12.8	3"	194	11.4	2"	291	18	3"
EAW-VD9106PA247I6-625AXSP08	-	220	-	187.7	376.9	-	222.5	168.2	190.3	375.3	363	18.8	3"	291	12.4	3"	436	26.5	3"
EAW-VD9106PA247I6-525AXSP08	-	208.5	155	177.4	361	-	210.8	158.5	179.8	359.8	303	18.1	3"	242	12	3"	363	25.4	3"
EAW-VD9106PA247I6-425AXSP08	-	190.5	140.6	161.6	333.6	116.7	192.7	143.8	163.8	333	242	17.5	3"	194	14.5	2"	291	24.5	3"
EAW-VD9108PA247I6-625AXSP06	-	292.6	-	249.6	501.3	-	296.3	-	252.9	499.1	484	20.1	3"	388	13.2	3"	581	24.1	4"
EAW-VD9108PA247I6-525AXSP06	-	275.8	204.8	234.6	478.1	-	279	209.1	237.8	476	400	18.7	3"	320	12.3	3"	480	26.3	3"
EAW-VD9108PA247I6-425AXSP06	146.20	249	183.9	211.3	437.3	152.5	252	188.1	214.4	436.6	315	17.6	3"	252	11.6	3"	378	24.7	3"
EAW-VD9110PA247I6-625AXSP06	233.90	376.9	285.3	322.6	635.1	240.4	378.8	288.8	325.3	631.5	484	23.6	3"	388	15.5	3"	581	29	4"
EAW-VD9110PA247I6-525AXSP04	-	333	-	282	587.9	-	339.8	-	288.2	587.8	606	15	4"	484	12.8	3"	727	21.1	4"
EAW-VD9110PA247I6-425AXSP04	-	303.9	-	256.3	543.2	-	309.5	228.7	262.5	543.2	484	17.1	3"	388	11.3	3"	581	20	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9112PA247I6-625AXSP04	-	436.4	-	372.1	748.2	-	442	-	377.8	746	727	18.3	4"	581	12.1	4"	872	25.7	4"
EAW-VD9112PA247I6-525AXSP04	-	413	306.7	351.3	717.2	-	418.4	313.7	356.2	713.9	606	17.3	4"	484	14.3	3"	727	24.4	4"
EAW-VD9112PA247I6-425AXSP04	-	376.9	278.1	319.4	662.1	230.7	381.4	284.3	324.6	659.9	484	19.4	3"	388	12.8	3"	581	23.2	4"
EAW-VD9114PA247I6-625AXSP04	-	520.6	392.2	445.2	882.6	-	524.8	398.4	449.7	877.7	727	20.6	4"	581	13.6	4"	872	29	4"
EAW-VD9114PA247I6-525AXSP02	-	-	-	-	777.5	-	-	-	-	782.7	1211	10.9	(2) 4"	969	7.2	(2) 4"	1453	15.3	(2) 4"
EAW-VD9114PA247I6-425AXSP02	-	-	-	-	714.8	-	-	-	-	720.5	969	10.1	(2) 4"	775	9.4	4"	1163	14.2	(2) 4"
EAW-VD9116PA247I6-625AXSP02	-	-	-	-	948.1	-	-	-	-	952.1	1453	13	(2) 4"	1163	8.6	(2) 4"	1744	18.3	(2) 4"
EAW-VD9116PA247I6-525AXSP02	-	-	-	-	904.2	-	-	-	-	907.3	1211	12.1	(2) 4"	969	7.9	(2) 4"	1453	17	(2) 4"
EAW-VD9116PA247I6-425AXSP02	-	449.9	-	-	832	-	465.1	-	-	835.5	969	11.3	(2) 4"	775	10.1	4"	1163	15.8	(2) 4"
EAW-VD9118PA247I6-625AXSP02	-	-	-	-	1080.5	-	-	-	-	1082.1	1453	14.2	(2) 4"	1163	9.3	(2) 4"	1744	20	(2) 4"
EAW-VD9118PA247I6-525AXSP02	-	574.2	-	-	1031.8	-	588.9	-	-	1032.2	1211	13.2	(2) 4"	969	8.7	(2) 4"	1453	18.6	(2) 4"
EAW-VD9118PA247I6-425AXSP02	-	522.6	-	-	948.4	-	536.2	-	452.2	950.5	969	12.4	(2) 4"	775	10.9	4"	1163	17.4	(2) 4"
EAW-VD9120PA247I6-625AXSP02	-	691.7	-	-	1213	-	706.7	-	-	1212.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD9120PA247I6-525AXSP02	-	653.1	-	-	1157.9	-	667	-	565.9	1158	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD9120PA247I6-425AXSP02	-	594.3	-	501.2	1065.8	-	606.9	-	512.8	1066.2	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD9102PJ247I6-625AXSP16	-	-	-	-	130.7	-	-	-	-	130.6	182	18.5	2"	145	12.2	2"	218	26	2"
EAW-VD9102PJ247I6-525AXSP16	-	68.6	-	-	122.4	-	70.2	-	-	122.4	145	17.4	2"	116	13.9	1-1/2"	174	24.4	2"
EAW-VD9102PJ247I6-425AXSP16	-	63.9	-	-	115.3	-	65.4	-	-	115.2	121	19.4	1-1/2"	97	12.7	1-1/2"	145	23.5	2"
EAW-VD9104PJ247I6-625AXSP12	-	159	119.9	136.2	269.5	-	160.2	121.7	137.2	267.8	242	20.3	3"	194	16.3	2"	291	28.5	3"
EAW-VD9104PJ247I6-525AXSP12	-	147.3	110	125.4	252.9	92	148.3	112	126.8	251.5	194	22.8	2"	155	15.1	2"	232	32.1	2"
EAW-VD9104PJ247I6-425AXSP08	-	127.1	-	-	229.5	-	130.1	-	-	229.4	242	13.9	3"	194	12.1	2"	291	19.5	3"
EAW-VD9106PJ247I6-625AXSP08	-	237.9	179.3	203.7	403.3	-	239.7	182	205.5	400.8	363	20.4	3"	291	13.5	3"	436	28.6	3"
EAW-VD9106PJ247I6-525AXSP08	-	224.9	168.5	191.8	386	140.9	226.7	171.3	193.7	383.7	303	19.6	3"	242	13	3"	363	27.6	3"
EAW-VD9106PJ247I6-425AXSP06	-	192.1	-	161.9	342.7	-	195.6	-	165.4	342	315	15.3	3"	252	10.1	3"	378	21.5	3"
EAW-VD9108PJ247I6-625AXSP06	-	316.8	238.3	270.8	537.1	-	318.7	242.3	273.3	533.8	484	21.6	3"	388	14.2	3"	581	26.3	4"
EAW-VD9108PJ247I6-525AXSP06	-	297.6	222.7	253.7	510.6	186	300	226.1	256.3	508.3	400	20.3	3"	320	13.4	3"	480	28.5	3"
EAW-VD9108PJ247I6-425AXSP04	-	251.4	-	-	454.7	-	257.5	-	-	455.4	484	15.8	3"	388	10.4	3"	581	18.2	4"
EAW-VD9110PJ247I6-625AXSP04	-	382.6	-	-	660	-	387.9	-	-	656.8	727	17.3	4"	581	11.4	4"	872	24.3	4"
EAW-VD9110PJ247I6-525AXSP04	-	361.4	-	306.4	629.7	-	366.3	-	311.9	627.9	606	16.3	4"	484	13.7	3"	727	22.9	4"
EAW-VD9110PJ247I6-425AXSP04	-	329	241.8	278.4	580.9	-	334	247.9	283.5	579.7	484	18.4	3"	388	12.1	3"	581	21.8	4"
EAW-VD9112PJ247I6-625AXSP04	-	472.6	355.3	403.8	801.8	-	476.2	361.3	407.6	796.8	727	19.8	4"	581	13.1	4"	872	27.9	4"
EAW-VD9112PJ247I6-525AXSP04	-	445.8	333.5	380	765.9	-	449.4	339.2	383.9	762.4	606	18.9	4"	484	15.4	3"	727	26.5	4"
EAW-VD9112PJ247I6-425AXSP02	-	-	-	-	644.6	-	-	-	-	649.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.7	(2) 4"
EAW-VD9114PJ247I6-625AXSP04	350.00	561.9	425.8	481.4	944.5	358.9	563.6	430.2	484.3	937.4	727	22.4	4"	581	14.8	4"	872	31.5	4"
EAW-VD9114PJ247I6-525AXSP02	-	-	-	-	837.5	-	-	-	-	840.5	1211	11.8	(2) 4"	969	7.8	(2) 4"	1453	16.6	(2) 4"
EAW-VD9114PJ247I6-425AXSP02	-	-	-	-	769.5	-	-	-	-	772.4	969	11	(2) 4"	775	10	4"	1163	15.5	(2) 4"
EAW-VD9116PJ247I6-625AXSP02	-	-	-	-	1020.9	-	-	-	-	1021.6	1453	14.1	(2) 4"	1163	9.2	(2) 4"	1744	19.8	(2) 4"
EAW-VD9116PJ247I6-525AXSP02	-	-	-	-	972.2	-	-	-	-	972.6	1211	13.1	(2) 4"	969	8.6	(2) 4"	1453	18.4	(2) 4"
EAW-VD9116PJ247I6-425AXSP02	-	491.6	-	-	893.8	-	504.1	-	-	894	969	12.3	(2) 4"	775	10.8	4"	1163	17.3	(2) 4"
EAW-VD9118PJ247I6-625AXSP02	-	-	-	-	1161.7	-	676.5	-	-	1159.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.6	(2) 4"
EAW-VD9118PJ247I6-525AXSP02	-	625.3	-	-	1105.9	-	637.6	-	-	1104.7	1211	14.4	(2) 4"	969	9.5	(2) 4"	1453	20.2	(2) 4"
EAW-VD9118PJ247I6-425AXSP02	-	567.8	-	479.2	1018.3	-	579.5	-	490.5	1016.7	969	13.6	(2) 4"	775	11.7	4"	1163	19.1	(2) 4"
EAW-VD91S1MA247I6-625AXSP16	-	-	-	-	70.2	-	-	-	-	70	109	18.2	1-1/2"	87	12	1-1/2"	131	25.6	1-1/2"
EAW-VD91S1MA247I6-525AXSP16	-	-	-	-	66.4	-	-	-	-	66.5	97	16.7	1-1/2"	78	11	1-1/2"	116	23.4	1-1/2"
EAW-VD91S1MA247I6-425AXSP16	-	33.9	-	-	61.4	-	34.8	-	-	61.4	73	16.5	1-1/2"	58	10.9	1-1/2"	87	23.2	1-1/2"
EAW-VD91S2MA247I6-625AXSP12	-	85.4	-	72.9	145.5	-	86.1	-	73.7	144.3	157	19.9	2"	126	15.7	1-1/2"	189	28	2"
EAW-VD91S2MA247I6-525AXSP12	-	81.6	61.1	69.6	139.6	-	82.1	62	70.2	138.6	121	22.9	1-1/2"	97	15.1	1-1/2"	145	28.7	2"
EAW-VD91S2MA247I6-425AXSP08	-	-	-	-	122.7	-	-	-	-	122.8	157	14	2"	126	11.8	1-1/2"	189	19.7	2"
EAW-VD91S3MA247I6-625AXSP08	-	126.2	-	107.7	215.6	-	127.4	-	109	213.9	230	21.2	2"	184	13.9	2"	276	24.3	3"
EAW-VD91S3MA247I6-525AXSP08	-	119.5	-	101.8	206.1	-	120.5	90.7	102.9	205	194	19.8	2"	155	13	2"	232	27.8	2"
EAW-VD91S3MA247I6-425AXSP08	-	109.5	81.1	93	191.3	-	110.6	82.7	94.2	190.2	157	18.6	2"	126	14.9	1-1/2"	189	26.2	2"
EAW-VD91S4MA247I6-625AXSP08	109.50	174.6	132.6	149.8	292.3	111.8	174.8	133.7	150.2	289.7	230	25.8	2"	184	17	2"	276	30.8	3"
EAW-VD91S4MA247I6-525AXSP06	-	157.7	-	134.2	272.3	-	159.1	119.5	135.7	270.8	254	16.9	3"	204	14.2	2"	305	23.7	3"
EAW-VD91S4MA247I6-425AXSP06	-	144	106.5	122.3	251.7	-	145.6	108.6	123.7	250.3	206	19.6	2"	165	12.9	2"	247	23.2	3"
EAW-VD91S5MA247I6-625AXSP06	-	218.6	165.8	187.5	367.1	-	219.4	167.4	188.3	363.8	315	21	3"	252	13.9	3"	378	29.5	3"
EAW-VD91S5MA247I6-525AXSP04	-	191.2	-	-	336.3	-	194.2	-	-	335	388	15.5	3"	310	10.2	3"	465	21.7	3"
EAW-VD91S5MA247I6-425AXSP04	-	174.8	-	147.8	311.4	-	178	-	150.8	310.6	315	14.6	3"	252	9.6	3"	378	20.5	3"
EAW-VD91S6MA247I6-625AXSP04	-	253.4	-	-	432.8	-	255.9	-	218.9	429.9	472	19.1	3"	378	12.5	3"	567	23	4"
EAW-VD91S6MA247I6-525AXSP04	-	236.9	-	201.6	409.5	-	239.3	179.6	203.9	407.3	388	17.8	3"	310	11.7	3"	465	25	3"
EAW-VD91S6MA247I6-425AXSP04	-	217.1	160.4	184.1	379.3	-	219	163.8	186.5	377.7	315	16.9	3"	252	11.1	3"	378	23.7	3"
EAW-FD91S1WK320P7-625AXSP16	-	55	-	47.1	92.9	-	55.2	42	47.3	91.9	91	23.7	2"	73	15.6	2"	109	33.3	2"
EAW-FD91S1WK320P7-525AXSP16	-	50.4	37.7	43	86.3	-	50.6	38.2	43.3	85.4	73	22.5	2"	58	17.3	1-1/2"	87	31.6	2"
EAW-FD91S1WK320P7-425AXSP12	-	43.5	-	36.7	77.2	-	44.1	-	37.4	76.8	79	17.7	2"	63	14.5	1-1/2"	94	24.9	2"
EAW-FD91S2WK320P7-625AXSP08	-	109.6	-	93.8	185.3	-	109.9	-	94.3	183.2	182	20.4	3"	145	13.5	3"	218	28.6	3"
EAW-FD91S2WK320P7-525AXSP08	-	102.3	76.8	87.5	175	-	102.8	77.7	88	173.3	151	19.6	3"	121	13	3"	182	27.6	3"
EAW-FD91S2WK320P7-425AXSP08	-	92.3	68.8	78.6	159.8	57.1	92.7	69.6	79.1	158.3	121	19	3"	97	15.5	2"	145	26.7	3"
EAW-FD91S3WK320P7-625AXSP06	-	166.5	126.2	142.7	279.3	-	166.5	127.1	142.9	276	242	23.6	3"	194	15.5	3"	291	29	4"
EAW-FD91S3WK320P7-525AXSP04	-	145.1	-	-	255.1	-	147.3	-	-	253.3	303	15	4"	242	12.8	3"	363	21.1	4"
EAW-FD91S3WK320P7-425AXSP04	-	130.5	-	-	232.4	-	132.7	-	112.5	231.1	242	17.1	3"	194	11.3	3"	291	20	4"
EAW-FD91S4WK320P7-625AXSP04	-	217.7	-	186.1	368.4	-	218.4	-	187.2	364.6	363	19.8	4"	291	13.1	4"	436	27.9	4"
EAW-FD91S4WK320P7-525AXSP04	-	203.2	152.2	173.3	347.8	-	203.9	154	174.3	344.3	303	18.9	4"	242	15.4	3"	363	26.5	4"
EAW-FD91S4WK320P7-425AXSP04	-	182.8	136.3	155.5	317.2	112.9	183.7	138.1	156.7	314.4	242	21	3"	194	13.8	3"	291	25.4	4"
EAW-FD91S5WK320P7-625AXSP04	175.80	279.4	212.8	239.8	466	179	278.6	213.6	239.5	460	363	23.7	4"	291	15.6	4"	436	33.3	4"
EAW-FD91S5WK320P7-525AXSP02	-	-	-	-	411.1	-	-	-	-	410.1	606	12.4	(2) 4"	484	8.2	(2) 4"	727	17.5	(2) 4"
EAW-FD91S5WK320P7-425AXSP02	-	-	-	-	372.9	-	-	-	-	372.8	484	11.6	(2) 4"	388	10.4	4"	581	16.4	(2) 4"
EAW-FD91S6WK320P7-625AXSP02	-	-	-	-	534.2	-	-	-	-	530.8	727	15.3	(2) 4"	581	10.1	(2) 4"	872	21.6	(2) 4"
EAW-FD91S6WK320P7-525AXSP02	-	284.8	-	-	502.8	-	289.5	-	-	500.1	606	14.4	(2) 4"	484	9.5	(2) 4"	727	20.2	(2) 4"
EAW-FD91S6WK320P7-425AXSP02	-	255.5	-	-	456.5	-	260	-	-	454.7	484	13.6	(2) 4"	388	11.7	4"	581	19.1	(2) 4"
EAW-FD15S1ZB370K4-625AXSP16	-	72.5	-	61.8	123.9	-	73.4	-	62.8	123.5	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB370K4-525AXSP16	-	67.4	50.1	57.3	116.9	-	68.3	51.3	58.2	116.7	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB370K4-425AXSP12	-	60.3	-	50.8	108.7	-	61.9	-	52.3	109	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB550K4-625AXSP16	-	79.3	59.3	67.7	136.1	-	80.5	60.7	68.7	136	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB550K4-525AXSP16	-	73.8	54.7	62.7	128.4	45.7	74.8	56.1	63.8	128.3	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB550K4-425AXSP12	-	66	-	55.5	119.4	-	67.7	-	57.2	119.8	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB750K4-625AXSP16	-	83.5	62.4	71.1	143.5	-	84.8	63.9	72.4	143.6	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB750K4-525AXSP12	-	74.8	-	63.1	134.1	-	76.9	-	65.1	134.8	133	15.6	3"	107	14	2"	160	21.9	3"
EAW-FD15S1ZB750K4-425AXSP12	-	69.7	-	58.6	126.3	-	71.7	52.5	60.4	127	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB370K5-625AXSP16	-	72.5	-	61.8	123.9	-	73.4	-	62.8	123.5	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB370K5-525AXSP16	-	67.4	50.1	57.3	116.9	-	68.3	51.3	58.2	116.7	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB370K5-425AXSP12	-	60.3	-	50.8	108.7	-	61.9	-	52.3	109	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB550K5-625AXSP16	-	79.3	59.3	67.7	136.1	-	80.5	60.7	68.7	136	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB550K5-525AXSP16	-	73.8	54.7	62.7	128.4	45.7	74.8	56.1	63.8	128.3	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB550K5-425AXSP12	-	66	-	55.5	119.4	-	67.7	-	57.2	119.8	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB750K5-625AXSP16	-	83.5	62.4	71.1	143.5	-	84.8	63.9	72.4	143.6	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB750K5-525AXSP12	-	74.8	-	63.1	134.1	-	76.9	-	65.1	134.8	133	15.6	3"	107	14	2"	160	21.9	3"
EAW-FD15S1ZB750K5-425AXSP12	-	69.7	-	58.6	126.3	-	71.7	52.5	60.4	127	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB370C4-625AXSP16	-	73.6	-	62.7	125.9	-	74.7	56.5	63.8	125.8	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB370C4-525AXSP16	-	69	51.3	58.7	119.7	-	70	52.5	59.7	119.7	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB370C4-425AXSP12	-	62.1	-	52.2	112	-	63.7	-	53.8	112.6	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB550C4-625AXSP16	-	82.3	61.6	70.2	141.6	-	83.7	63.1	71.5	141.6	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB550C4-525AXSP12	-	74	-	62.3	132.4	-	76.1	-	64.3	133.2	133	15.6	3"	107	14	2"	160	21.9	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1ZB550C4-425AXSP12	-	68.9	-	57.9	124.7	-	70.8	51.8	59.7	125.4	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB370C5-625AXSP16	-	73.6	-	62.7	125.9	-	74.7	56.5	63.8	125.8	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB370C5-525AXSP16	-	69	51.3	58.7	119.7	-	70	52.5	59.7	119.7	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB370C5-425AXSP12	-	62.1	-	52.2	112	-	63.7	-	53.8	112.6	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB550C5-625AXSP16	-	82.3	61.6	70.2	141.6	-	83.7	63.1	71.5	141.6	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB550C5-525AXSP12	-	74	-	62.3	132.4	-	76.1	-	64.3	133.2	133	15.6	3"	107	14	2"	160	21.9	3"
EAW-FD15S1ZB550C5-425AXSP12	-	68.9	-	57.9	124.7	-	70.8	51.8	59.7	125.4	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB370K8-625AXSP16	-	72.5	-	61.8	123.9	-	73.4	-	62.8	123.5	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB370K8-525AXSP16	-	67.4	50.1	57.3	116.9	-	68.3	51.3	58.2	116.7	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB370K8-425AXSP12	-	60.3	-	50.8	108.7	-	61.9	-	52.3	109	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB550K8-625AXSP16	-	79.3	59.3	67.7	136.1	-	80.5	60.7	68.7	136	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB550K8-525AXSP16	-	73.8	54.7	62.7	128.4	45.7	74.8	56.1	63.8	128.3	97	22.8	2"	78	15	2"	116	32	2"
EAW-FD15S1ZB550K8-425AXSP12	-	66	-	55.5	119.4	-	67.7	-	57.2	119.8	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S1ZB750K8-625AXSP16	-	83.5	62.4	71.1	143.5	-	84.8	63.9	72.4	143.6	121	20.1	3"	97	16.4	2"	145	28.2	3"
EAW-FD15S1ZB750K8-525AXSP12	-	74.8	-	63.1	134.1	-	76.9	-	65.1	134.8	133	15.6	3"	107	14	2"	160	21.9	3"
EAW-FD15S1ZB750K8-425AXSP12	-	69.7	-	58.6	126.3	-	71.7	52.5	60.4	127	109	19	2"	87	12.5	2"	131	21.2	3"
EAW-FD15S2ZB370K4-625AXSP08	-	144.3	-	123.1	247.1	-	146.1	-	125	246.4	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB370K4-525AXSP08	-	136.6	101.5	116.2	236.6	-	138.4	103.8	118	236	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB370K4-425AXSP08	-	126.9	93.9	107.9	222.5	78	128.8	96	109.6	222.5	164	18.5	3"	131	12.2	3"	196	25.9	3"
EAW-FD15S2ZB550K4-625AXSP08	-	158	118.1	134.8	271.5	-	160.4	120.9	136.9	271.2	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB550K4-525AXSP08	-	149.4	110.9	127	259.8	92.6	151.5	113.5	129.1	259.5	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB550K4-425AXSP06	-	131	-	110.2	237.2	-	134.5	-	113.5	238.1	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB750K4-625AXSP08	-	166.2	124.1	141.6	286.2	-	168.8	127.2	144.1	286.4	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB750K4-525AXSP08	93.30	157.7	116.9	133.8	274.5	97.7	160.1	119.9	136.5	275	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB750K4-425AXSP06	-	138.4	-	116.4	250.8	-	142.2	104	120	252.3	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB370K5-625AXSP08	-	144.3	-	123.1	247.1	-	146.1	-	125	246.4	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB370K5-525AXSP08	-	136.6	101.5	116.2	236.6	-	138.4	103.8	118	236	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB370K5-425AXSP08	-	126.9	93.9	107.9	222.5	78	128.8	96	109.6	222.5	164	18.5	3"	131	12.2	3"	196	25.9	3"
EAW-FD15S2ZB550K5-625AXSP08	-	158	118.1	134.8	271.5	-	160.4	120.9	136.9	271.2	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB550K5-525AXSP08	-	149.4	110.9	127	259.8	92.6	151.5	113.5	129.1	259.5	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB550K5-425AXSP06	-	131	-	110.2	237.2	-	134.5	-	113.5	238.1	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB750K5-625AXSP08	-	166.2	124.1	141.6	286.2	-	168.8	127.2	144.1	286.4	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB750K5-525AXSP08	93.30	157.7	116.9	133.8	274.5	97.7	160.1	119.9	136.5	275	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB750K5-425AXSP06	-	138.4	-	116.4	250.8	-	142.2	104	120	252.3	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB370C4-625AXSP08	-	146.6	-	125	250.8	-	148.7	112.4	127.1	250.9	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB370C4-525AXSP08	-	139.7	103.9	118.8	242.4	-	141.7	106.4	121	242.4	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB370C4-425AXSP06	-	123.3	-	103.6	222.9	-	126.5	-	106.9	223.7	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB550C4-625AXSP08	-	164	122.5	139.7	282.2	-	166.6	125.6	142.3	282.6	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB550C4-525AXSP08	-	155.8	115.6	132.3	271.1	96.5	158.2	118.4	134.8	271.4	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB550C4-425AXSP06	-	136.9	-	115	248.2	-	140.6	102.9	118.6	249.1	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB370C5-625AXSP08	-	146.6	-	125	250.8	-	148.7	112.4	127.1	250.9	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB370C5-525AXSP08	-	139.7	103.9	118.8	242.4	-	141.7	106.4	121	242.4	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB370C5-425AXSP06	-	123.3	-	103.6	222.9	-	126.5	-	106.9	223.7	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB550C5-625AXSP08	-	164	122.5	139.7	282.2	-	166.6	125.6	142.3	282.6	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB550C5-525AXSP08	-	155.8	115.6	132.3	271.1	96.5	158.2	118.4	134.8	271.4	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB550C5-425AXSP06	-	136.9	-	115	248.2	-	140.6	102.9	118.6	249.1	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB370K8-625AXSP08	-	144.3	-	123.1	247.1	-	146.1	-	125	246.4	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB370K8-525AXSP08	-	136.6	101.5	116.2	236.6	-	138.4	103.8	118	236	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB370K8-425AXSP08	-	126.9	93.9	107.9	222.5	78	128.8	96	109.6	222.5	164	18.5	3"	131	12.2	3"	196	25.9	3"
EAW-FD15S2ZB550K8-625AXSP08	-	158	118.1	134.8	271.5	-	160.4	120.9	136.9	271.2	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB550K8-525AXSP08	-	149.4	110.9	127	259.8	92.6	151.5	113.5	129.1	259.5	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB550K8-425AXSP06	-	131	-	110.2	237.2	-	134.5	-	113.5	238.1	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S2ZB750K8-625AXSP08	-	166.2	124.1	141.6	286.2	-	168.8	127.2	144.1	286.4	242	20.9	3"	194	13.8	3"	291	25.1	4"
EAW-FD15S2ZB750K8-525AXSP08	93.30	157.7	116.9	133.8	274.5	97.7	160.1	119.9	136.5	275	200	19.5	3"	160	12.8	3"	240	27.4	3"
EAW-FD15S2ZB750K8-425AXSP06	-	138.4	-	116.4	250.8	-	142.2	104	120	252.3	218	15.9	3"	174	10.5	3"	262	18.9	4"
EAW-FD15S3ZB370K4-625AXSP06	-	221	166.4	188.8	374.3	-	223	169.2	191	373.2	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB370K4-525AXSP06	127.20	210.2	157.3	179.2	360.7	131.9	212.2	160.1	181.2	359.6	272	19.4	4"	218	15.3	3"	327	27.2	4"
EAW-FD15S3ZB370K4-425AXSP04	-	178.2	-	-	322.5	-	182.9	-	154.4	323.1	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB550K4-625AXSP06	-	241.8	181.9	206.8	411.9	153.2	244.6	185.2	209.3	410.9	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB550K4-525AXSP04	-	211.9	-	-	379.8	-	217.7	-	-	381.2	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB550K4-425AXSP04	-	194.9	-	163.8	353.4	-	200.3	-	168.9	354.8	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB750K4-625AXSP04	-	235.6	-	-	418.3	-	242.2	-	-	419.8	490	13.1	(2) 4"	392	11.5	4"	589	18.5	(2) 4"
EAW-FD15S3ZB750K4-525AXSP04	-	223.4	-	188	401.2	-	229.9	-	194.2	403.1	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB750K4-425AXSP04	-	206	-	173	374.4	-	211.7	154.8	178.6	375.9	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB370K5-625AXSP06	-	221	166.4	188.8	374.3	-	223	169.2	191	373.2	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB370K5-525AXSP06	127.20	210.2	157.3	179.2	360.7	131.9	212.2	160.1	181.2	359.6	272	19.4	4"	218	15.3	3"	327	27.2	4"
EAW-FD15S3ZB370K5-425AXSP04	-	178.2	-	-	322.5	-	182.9	-	154.4	323.1	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB550K5-625AXSP06	-	241.8	181.9	206.8	411.9	153.2	244.6	185.2	209.3	410.9	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB550K5-525AXSP04	-	211.9	-	-	379.8	-	217.7	-	-	381.2	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB550K5-425AXSP04	-	194.9	-	163.8	353.4	-	200.3	-	168.9	354.8	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB750K5-625AXSP04	-	235.6	-	-	418.3	-	242.2	-	-	419.8	490	13.1	(2) 4"	392	11.5	4"	589	18.5	(2) 4"
EAW-FD15S3ZB750K5-525AXSP04	-	223.4	-	188	401.2	-	229.9	-	194.2	403.1	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB750K5-425AXSP04	-	206	-	173	374.4	-	211.7	154.8	178.6	375.9	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB370C4-625AXSP06	-	224.2	168.7	191.8	380.4	-	226.7	172.2	194.3	380.1	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB370C4-525AXSP06	130.20	215.1	161	183.5	369.6	135.1	217.8	164.1	185.9	368.9	272	19.4	4"	218	15.3	3"	327	27.2	4"
EAW-FD15S3ZB370C4-425AXSP04	-	183.5	-	154.3	332.3	-	188.4	-	159.1	333.5	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB550C4-625AXSP06	153.00	251.3	188.6	214.4	428.1	159.1	254.2	192.5	217.6	428.1	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB550C4-525AXSP04	-	220.8	-	-	396.1	-	227.1	-	191.9	398.5	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB550C4-425AXSP04	-	203.6	-	171.2	369.8	-	209.2	153.2	176.4	371.8	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB370C5-625AXSP06	-	224.2	168.7	191.8	380.4	-	226.7	172.2	194.3	380.1	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB370C5-525AXSP06	130.20	215.1	161	183.5	369.6	135.1	217.8	164.1	185.9	368.9	272	19.4	4"	218	15.3	3"	327	27.2	4"
EAW-FD15S3ZB370C5-425AXSP04	-	183.5	-	154.3	332.3	-	188.4	-	159.1	333.5	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB550C5-625AXSP06	153.00	251.3	188.6	214.4	428.1	159.1	254.2	192.5	217.6	428.1	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB550C5-525AXSP04	-	220.8	-	-	396.1	-	227.1	-	191.9	398.5	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB550C5-425AXSP04	-	203.6	-	171.2	369.8	-	209.2	153.2	176.4	371.8	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB370K8-625AXSP06	-	221	166.4	188.8	374.3	-	223	169.2	191	373.2	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB370K8-525AXSP06	127.20	210.2	157.3	179.2	360.7	131.9	212.2	160.1	181.2	359.6	272	19.4	4"	218	15.3	3"	327	27.2	4"
EAW-FD15S3ZB370K8-425AXSP04	-	178.2	-	-	322.5	-	182.9	-	154.4	323.1	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB550K8-625AXSP06	-	241.8	181.9	206.8	411.9	153.2	244.6	185.2	209.3	410.9	327	20.2	4"	262	13.3	4"	392	28.3	4"
EAW-FD15S3ZB550K8-525AXSP04	-	211.9	-	-	379.8	-	217.7	-	-	381.2	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB550K8-425AXSP04	-	194.9	-	163.8	353.4	-	200.3	-	168.9	354.8	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S3ZB750K8-625AXSP04	-	235.6	-	-	418.3	-	242.2	-	-	419.8	490	13.1	(2) 4"	392	11.5	4"	589	18.5	(2) 4"
EAW-FD15S3ZB750K8-525AXSP04	-	223.4	-	188	401.2	-	229.9	-	194.2	403.1	406	15.7	4"	325	10.3	4"	487	17.8	(2) 4"
EAW-FD15S3ZB750K8-425AXSP04	-	206	-	173	374.4	-	211.7	154.8	178.6	375.9	327	14.3	4"	262	9.4	4"	392	20.1	4"
EAW-FD15S4ZB370K4-625AXSP04	-	287.8	-	245.6	493.1	-	291.9	-	249.6	492.3	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB370K4-525AXSP04	-	272.7	202.6	231.9	473.3	-	276.3	207.5	235.6	472	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB370K4-425AXSP04	-	251.6	185.8	213.3	441.6	154.3	255	190.2	216.7	440.9	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB550K4-625AXSP04	-	315.6	235.4	268.7	542.3	-	319.9	241	273.4	541.8	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB550K4-525AXSP04	-	298.4	221.4	253.6	519.6	-	303	227	258.2	519.7	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB550K4-425AXSP04	160.80	274.8	202.7	233	484.5	168.3	279.2	207.8	237	484.5	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB750K4-625AXSP04	-	332	247.4	282.3	571.7	-	337.1	253.5	287.8	572	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S4ZB750K4-525AXSP04	-	314.9	233.4	267.7	549	194.9	320.3	239.3	272.4	549.9	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB750K4-425AXSP02	-	-	-	-	461.8	-	-	-	-	468.7	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.4	(2) 4"
EAW-FD15S4ZB370K5-625AXSP04	-	287.8	-	245.6	493.1	-	291.9	-	249.6	492.3	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB370K5-525AXSP04	-	272.7	202.6	231.9	473.3	-	276.3	207.5	235.6	472	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB370K5-425AXSP04	-	251.6	185.8	213.3	441.6	154.3	255	190.2	216.7	440.9	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB550K5-625AXSP04	-	315.6	235.4	268.7	542.3	-	319.9	241	273.4	541.8	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB550K5-525AXSP04	-	298.4	221.4	253.6	519.6	-	303	227	258.2	519.7	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB550K5-425AXSP04	160.80	274.8	202.7	233	484.5	168.3	279.2	207.8	237	484.5	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB750K5-625AXSP04	-	332	247.4	282.3	571.7	-	337.1	253.5	287.8	572	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB750K5-525AXSP04	-	314.9	233.4	267.7	549	194.9	320.3	239.3	272.4	549.9	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB750K5-425AXSP02	-	-	-	-	461.8	-	-	-	-	468.7	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.4	(2) 4"
EAW-FD15S4ZB370C4-625AXSP04	-	292.4	-	249.3	501	-	297.1	-	253.9	501.3	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB370C4-525AXSP04	-	279	207.4	237.2	484.8	-	283.5	212.7	241.6	484.7	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB370C4-425AXSP04	151.70	258.8	191.1	219.6	455.2	158.7	262.8	195.7	223.1	455.2	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB550C4-625AXSP04	-	327.5	244.2	279	563.6	-	332.8	250.4	284.2	564.4	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB550C4-525AXSP04	-	311.1	230.7	264.1	542.1	192.7	316.3	236.5	269.2	542.8	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB550C4-425AXSP02	-	-	-	-	456.4	-	-	-	-	463.8	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.4	(2) 4"
EAW-FD15S4ZB370C5-625AXSP04	-	292.4	-	249.3	501	-	297.1	-	253.9	501.3	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB370C5-525AXSP04	-	279	207.4	237.2	484.8	-	283.5	212.7	241.6	484.7	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB370C5-425AXSP04	151.70	258.8	191.1	219.6	455.2	158.7	262.8	195.7	223.1	455.2	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB550C5-625AXSP04	-	327.5	244.2	279	563.6	-	332.8	250.4	284.2	564.4	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB550C5-525AXSP04	-	311.1	230.7	264.1	542.1	192.7	316.3	236.5	269.2	542.8	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB550C5-425AXSP02	-	-	-	-	456.4	-	-	-	-	463.8	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.4	(2) 4"
EAW-FD15S4ZB370K8-625AXSP04	-	287.8	-	245.6	493.1	-	291.9	-	249.6	492.3	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB370K8-525AXSP04	-	272.7	202.6	231.9	473.3	-	276.3	207.5	235.6	472	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB370K8-425AXSP04	-	251.6	185.8	213.3	441.6	154.3	255	190.2	216.7	440.9	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB550K8-625AXSP04	-	315.6	235.4	268.7	542.3	-	319.9	241	273.4	541.8	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB550K8-525AXSP04	-	298.4	221.4	253.6	519.6	-	303	227	258.2	519.7	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB550K8-425AXSP04	160.80	274.8	202.7	233	484.5	168.3	279.2	207.8	237	484.5	327	17.8	4"	262	11.7	4"	392	25	4"
EAW-FD15S4ZB750K8-625AXSP04	-	332	247.4	282.3	571.7	-	337.1	253.5	287.8	572	490	16.6	(2) 4"	392	13.8	4"	589	23.3	(2) 4"
EAW-FD15S4ZB750K8-525AXSP04	-	314.9	233.4	267.7	549	194.9	320.3	239.3	272.4	549.9	406	19.2	4"	325	12.6	4"	487	22.7	(2) 4"
EAW-FD15S4ZB750K8-425AXSP02	-	-	-	-	461.8	-	-	-	-	468.7	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.4	(2) 4"
EAW-FD15S5ZB370K4-625AXSP04	230.10	370.8	280.7	317.9	625.4	236.9	373.7	284.5	320.5	622.8	490	20.1	(2) 4"	392	16.1	4"	589	28.2	(2) 4"
EAW-FD15S5ZB370K4-525AXSP02	-	-	-	-	557.1	-	-	-	-	560.8	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370K4-425AXSP02	-	-	-	-	516.1	-	-	-	-	519.3	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB550K4-625AXSP02	-	-	-	-	638.5	-	-	-	-	642.7	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB550K4-525AXSP02	-	-	-	-	611.2	-	-	-	-	616.5	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550K4-425AXSP02	-	-	-	-	565.6	-	314.1	-	-	570.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB750K4-625AXSP02	-	-	-	-	672.4	-	-	-	-	678	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB750K4-525AXSP02	-	-	-	-	645	-	-	-	-	651.6	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB750K4-425AXSP02	-	318.8	-	-	597.4	-	332.1	-	-	603.6	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB370K5-625AXSP04	230.10	370.8	280.7	317.9	625.4	236.9	373.7	284.5	320.5	622.8	490	20.1	(2) 4"	392	16.1	4"	589	28.2	(2) 4"
EAW-FD15S5ZB370K5-525AXSP02	-	-	-	-	557.1	-	-	-	-	560.8	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370K5-425AXSP02	-	-	-	-	516.1	-	-	-	-	519.3	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB550K5-625AXSP02	-	-	-	-	638.5	-	-	-	-	642.7	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB550K5-525AXSP02	-	-	-	-	611.2	-	-	-	-	616.5	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550K5-425AXSP02	-	-	-	-	565.6	-	314.1	-	-	570.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB750K5-625AXSP02	-	-	-	-	672.4	-	-	-	-	678	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB750K5-525AXSP02	-	-	-	-	645	-	-	-	-	651.6	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB750K5-425AXSP02	-	318.8	-	-	597.4	-	332.1	-	-	603.6	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB370C4-625AXSP04	233.20	376.7	285	322.4	635.6	240.9	380.4	289.5	326.1	634.2	490	20.1	(2) 4"	392	16.1	4"	589	28.2	(2) 4"
EAW-FD15S5ZB370C4-525AXSP02	-	-	-	-	570.3	-	-	-	-	575.7	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370C4-425AXSP02	-	-	-	-	531.5	-	-	-	-	535.7	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB550C4-625AXSP02	-	-	-	-	663.1	-	-	-	-	669.1	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB550C4-525AXSP02	-	-	-	-	638	-	-	-	-	643.3	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550C4-425AXSP02	-	315	-	-	591.3	-	328.3	-	-	596.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB370C5-625AXSP04	233.20	376.7	285	322.4	635.6	240.9	380.4	289.5	326.1	634.2	490	20.1	(2) 4"	392	16.1	4"	589	28.2	(2) 4"
EAW-FD15S5ZB370C5-525AXSP02	-	-	-	-	570.3	-	-	-	-	575.7	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370C5-425AXSP02	-	-	-	-	531.5	-	-	-	-	535.7	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB550C5-625AXSP02	-	-	-	-	663.1	-	-	-	-	669.1	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB550C5-525AXSP02	-	-	-	-	638	-	-	-	-	643.3	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550C5-425AXSP02	-	315	-	-	591.3	-	328.3	-	-	596.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB370K8-625AXSP04	230.10	370.8	280.7	317.9	625.4	236.9	373.7	284.5	320.5	622.8	490	20.1	(2) 4"	392	16.1	4"	589	28.2	(2) 4"
EAW-FD15S5ZB370K8-525AXSP02	-	-	-	-	557.1	-	-	-	-	560.8	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370K8-425AXSP02	-	-	-	-	516.1	-	-	-	-	519.3	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB550K8-625AXSP02	-	-	-	-	638.5	-	-	-	-	642.7	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB550K8-525AXSP02	-	-	-	-	611.2	-	-	-	-	616.5	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550K8-425AXSP02	-	-	-	-	565.6	-	314.1	-	-	570.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S5ZB750K8-625AXSP02	-	-	-	-	672.4	-	-	-	-	678	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.8	(3) 4"
EAW-FD15S5ZB750K8-525AXSP02	-	-	-	-	645	-	-	-	-	651.6	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB750K8-425AXSP02	-	318.8	-	-	597.4	-	332.1	-	-	603.6	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.8	(2) 4"
EAW-FD15S6ZB370K4-625AXSP02	-	-	-	-	712.2	-	-	-	-	714.2	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB370K4-525AXSP02	-	380.5	-	-	682.9	-	390.8	-	-	685.2	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB370K4-425AXSP02	-	348.3	-	-	632.7	-	357.9	-	-	635.2	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB550K4-625AXSP02	-	-	-	-	781.7	-	-	-	-	785.4	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB550K4-525AXSP02	-	416.6	-	-	749.8	-	428.4	-	-	752.7	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB550K4-425AXSP02	-	381.1	-	319.6	693.9	-	391.5	-	330.2	696.9	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB750K4-625AXSP02	-	461.7	-	-	823.4	-	475.7	-	-	827.7	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB750K4-525AXSP02	-	439	-	-	791.7	-	452.1	-	382.2	797	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB750K4-425AXSP02	-	402.3	-	337.6	734.7	-	414.4	-	349	738.1	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB370C4-625AXSP02	-	-	-	-	723.7	-	-	-	-	727.2	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB370C4-525AXSP02	-	389.7	-	-	699.3	-	400.7	-	-	702.6	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB370C4-425AXSP02	-	358.6	-	-	652.8	-	369.2	-	311.2	655.4	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB550C4-625AXSP02	-	455.6	-	-	813	-	469.7	-	-	817.8	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB550C4-525AXSP02	-	433.9	-	-	781.9	-	446.7	-	-	786.8	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB550C4-425AXSP02	-	397.8	-	333.7	725.8	-	409.6	-	345.1	730.1	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB370C5-625AXSP02	-	-	-	-	723.7	-	-	-	-	727.2	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB370C5-525AXSP02	-	389.7	-	-	699.3	-	400.7	-	-	702.6	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB370C5-425AXSP02	-	358.6	-	-	652.8	-	369.2	-	311.2	655.4	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB550C5-625AXSP02	-	455.6	-	-	813	-	469.7	-	-	817.8	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB550C5-525AXSP02	-	433.9	-	-	781.9	-	446.7	-	-	786.8	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB550C5-425AXSP02	-	397.8	-	333.7	725.8	-	409.6	-	345.1	730.1	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S6ZB370K8-625AXSP02	-	-	-	-	712.2	-	-	-	-	714.2	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB370K8-525AXSP02	-	380.5	-	-	682.9	-	390.8	-	-	685.2	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB370K8-425AXSP02	-	348.3	-	-	632.7	-	357.9	-	-	635.2	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB550K8-625AXSP02	-	-	-	-	781.7	-	-	-	-	785.4	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB550K8-525AXSP02	-	416.6	-	-	749.8	-	428.4	-	-	752.7	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB550K8-425AXSP02	-	381.1	-	319.6	693.9	-	391.5	-	330.2	696.9	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S6ZB750K8-625AXSP02	-	461.7	-	-	823.4	-	475.7	-	-	827.7	981	13.7	(3) 4"	785	11.1	(2) 4"	1177	19.2	(3) 4"
EAW-FD15S6ZB750K8-525AXSP02	-	439	-	-	791.7	-	452.1	-	382.2	797	818	15.1	(2) 4"	654	10	(2) 4"	981	18.1	(3) 4"
EAW-FD15S6ZB750K8-425AXSP02	-	402.3	-	337.6	734.7	-	414.4	-	349	738.1	654	13.7	(2) 4"	523	9	(2) 4"	785	19.2	(2) 4"
EAW-FD15S1ZK370K4-625AXSP16	-	78.6	59.2	67.3	133.2	-	79.3	60.2	67.9	132.6	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK370K4-525AXSP16	-	73.2	54.7	62.3	125.7	45.8	73.8	55.7	63	125.2	97	24.3	2"	78	16	2"	116	34.2	2"
EAW-FD15S1ZK370K4-425AXSP12	-	65.8	-	55.6	117	-	67.1	-	56.8	117	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK550K4-625AXSP16	-	86.7	65.1	74.1	147.3	-	87.4	66.4	74.8	146.7	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK550K4-525AXSP12	-	77.9	-	65.9	137.3	-	79.4	-	67.5	137.4	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK550K4-425AXSP12	-	72.3	52.7	61	129.1	-	73.8	54.4	62.4	129.1	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK750K4-625AXSP12	-	87.9	-	-	153.5	-	89.8	-	76.4	153.8	164	17.4	3"	131	11.5	3"	196	24.5	3"
EAW-FD15S1ZK750K4-525AXSP12	-	82.6	-	69.8	145.9	-	84.2	62.5	71.5	146.2	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK750K4-425AXSP12	-	76.7	55.9	64.7	137.1	-	78.3	57.8	66.3	137.5	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK370K5-625AXSP16	-	78.6	59.2	67.3	133.2	-	79.3	60.2	67.9	132.6	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK370K5-525AXSP16	-	73.2	54.7	62.3	125.7	45.8	73.8	55.7	63	125.2	97	24.3	2"	78	16	2"	116	34.2	2"
EAW-FD15S1ZK370K5-425AXSP12	-	65.8	-	55.6	117	-	67.1	-	56.8	117	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK550K5-625AXSP16	-	86.7	65.1	74.1	147.3	-	87.4	66.4	74.8	146.7	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK550K5-525AXSP12	-	77.9	-	65.9	137.3	-	79.4	-	67.5	137.4	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK550K5-425AXSP12	-	72.3	52.7	61	129.1	-	73.8	54.4	62.4	129.1	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK750K5-625AXSP12	-	87.9	-	-	153.5	-	89.8	-	76.4	153.8	164	17.4	3"	131	11.5	3"	196	24.5	3"
EAW-FD15S1ZK750K5-525AXSP12	-	82.6	-	69.8	145.9	-	84.2	62.5	71.5	146.2	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK750K5-425AXSP12	-	76.7	55.9	64.7	137.1	-	78.3	57.8	66.3	137.5	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK370C4-625AXSP16	-	80.6	60.7	68.9	136.7	-	81.5	61.8	69.8	136.3	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK370C4-525AXSP12	-	73	-	61.8	128.6	-	74.4	-	63.3	128.6	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK370C4-425AXSP12	-	68	-	57.5	121.1	-	69.4	51.3	58.7	121.2	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK550C4-625AXSP16	-	90.4	68	77.3	154.2	57.3	91.5	69.3	78.3	153.9	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK550C4-525AXSP12	-	81.5	-	69	144.2	-	83.2	61.8	70.6	144.3	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK550C4-425AXSP12	-	75.6	55.1	63.8	135.2	-	77.2	56.9	65.3	135.4	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK750C4-525AXSP12	-	84.8	62.2	71.7	150.1	-	86.8	64.3	73.6	150.6	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK750C4-425AXSP12	-	79	57.6	66.6	141.4	-	80.8	59.6	68.4	141.8	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK370C5-625AXSP16	-	80.6	60.7	68.9	136.7	-	81.5	61.8	69.8	136.3	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK370C5-525AXSP12	-	73	-	61.8	128.6	-	74.4	-	63.3	128.6	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK370C5-425AXSP12	-	68	-	57.5	121.1	-	69.4	51.3	58.7	121.2	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK550C5-625AXSP16	-	90.4	68	77.3	154.2	57.3	91.5	69.3	78.3	153.9	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK550C5-525AXSP12	-	81.5	-	69	144.2	-	83.2	61.8	70.6	144.3	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK550C5-425AXSP12	-	75.6	55.1	63.8	135.2	-	77.2	56.9	65.3	135.4	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK750C5-525AXSP12	-	84.8	62.2	71.7	150.1	-	86.8	64.3	73.6	150.6	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK750C5-425AXSP12	-	79	57.6	66.6	141.4	-	80.8	59.6	68.4	141.8	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK370K8-625AXSP16	-	78.6	59.2	67.3	133.2	-	79.3	60.2	67.9	132.6	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK370K8-525AXSP16	-	73.2	54.7	62.3	125.7	45.8	73.8	55.7	63	125.2	97	24.3	2"	78	16	2"	116	34.2	2"
EAW-FD15S1ZK370K8-425AXSP12	-	65.8	-	55.6	117	-	67.1	-	56.8	117	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK550K8-625AXSP16	-	86.7	65.1	74.1	147.3	-	87.4	66.4	74.8	146.7	121	21.6	3"	97	17.4	2"	145	30.3	3"
EAW-FD15S1ZK550K8-525AXSP12	-	77.9	-	65.9	137.3	-	79.4	-	67.5	137.4	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK550K8-425AXSP12	-	72.3	52.7	61	129.1	-	73.8	54.4	62.4	129.1	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S1ZK750K8-625AXSP12	-	87.9	-	-	153.5	-	89.8	-	76.4	153.8	164	17.4	3"	131	11.5	3"	196	24.5	3"
EAW-FD15S1ZK750K8-525AXSP12	-	82.6	-	69.8	145.9	-	84.2	62.5	71.5	146.2	133	16.7	3"	107	14.8	2"	160	23.5	3"
EAW-FD15S1ZK750K8-425AXSP12	-	76.7	55.9	64.7	137.1	-	78.3	57.8	66.3	137.5	109	20.2	2"	87	13.3	2"	131	22.8	3"
EAW-FD15S2ZK370K4-625AXSP08	-	156.8	118	134	265.7	-	158	120	135.3	264.2	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK370K4-525AXSP08	-	148.2	110.9	126.3	254.1	92.8	149.4	112.8	127.6	253.1	200	21	3"	160	13.9	3"	240	29.5	3"
EAW-FD15S2ZK370K4-425AXSP06	-	130.7	-	110.4	232.6	-	133.3	-	112.8	232.5	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK550K4-625AXSP08	-	172.6	129.8	147.5	293.5	-	174.3	132.1	149.2	292.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK550K4-525AXSP06	-	156.7	-	132.4	276.6	-	159.8	-	135.7	276.7	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK550K4-425AXSP06	-	143.5	104.6	121.1	256.6	-	146.4	108.1	124.1	256.6	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK750K4-625AXSP08	-	182.4	137.1	155.9	311.3	115.5	184.7	139.7	158	310.7	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK750K4-525AXSP06	-	165.9	-	140.4	293.8	-	169.5	-	143.9	294.1	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK750K4-425AXSP06	-	152.2	110.9	128.5	272.5	-	155.5	114.7	131.7	273.2	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK370K5-625AXSP08	-	156.8	118	134	265.7	-	158	120	135.3	264.2	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK370K5-525AXSP08	-	148.2	110.9	126.3	254.1	92.8	149.4	112.8	127.6	253.1	200	21	3"	160	13.9	3"	240	29.5	3"
EAW-FD15S2ZK370K5-425AXSP06	-	130.7	-	110.4	232.6	-	133.3	-	112.8	232.5	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK550K5-625AXSP08	-	172.6	129.8	147.5	293.5	-	174.3	132.1	149.2	292.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK550K5-525AXSP06	-	156.7	-	132.4	276.6	-	159.8	-	135.7	276.7	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK550K5-425AXSP06	-	143.5	104.6	121.1	256.6	-	146.4	108.1	124.1	256.6	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK750K5-625AXSP08	-	182.4	137.1	155.9	311.3	115.5	184.7	139.7	158	310.7	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK750K5-525AXSP06	-	165.9	-	140.4	293.8	-	169.5	-	143.9	294.1	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK750K5-425AXSP06	-	152.2	110.9	128.5	272.5	-	155.5	114.7	131.7	273.2	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK370C4-625AXSP08	-	160.6	120.9	137.4	272.4	-	162.3	123.1	139.1	271.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK370C4-525AXSP08	-	152.6	114.2	130.2	262.4	95.7	154.1	116.2	131.8	261.4	200	21	3"	160	13.9	3"	240	29.5	3"
EAW-FD15S2ZK370C4-425AXSP06	-	135	-	114	240.7	-	137.8	101.8	116.8	241	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK550C4-625AXSP08	-	180.1	135.4	154	307.2	114.1	182.3	138	155.9	306.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK550C4-525AXSP06	-	163.9	-	138.8	290	-	167.4	-	142.2	290.6	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK550C4-425AXSP06	-	150.3	109.3	126.6	268.7	-	153.3	113.1	129.7	269	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK750C4-525AXSP06	-	170.5	-	144.4	302	-	174.6	129.5	148.1	303.3	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK750C4-425AXSP06	-	156.8	114.2	132.3	281.4	-	160.4	118.1	135.6	282.3	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK370C5-625AXSP08	-	160.6	120.9	137.4	272.4	-	162.3	123.1	139.1	271.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK370C5-525AXSP08	-	152.6	114.2	130.2	262.4	95.7	154.1	116.2	131.8	261.4	200	21	3"	160	13.9	3"	240	29.5	3"
EAW-FD15S2ZK370C5-425AXSP06	-	135	-	114	240.7	-	137.8	101.8	116.8	241	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK550C5-625AXSP08	-	180.1	135.4	154	307.2	114.1	182.3	138	155.9	306.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK550C5-525AXSP06	-	163.9	-	138.8	290	-	167.4	-	142.2	290.6	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK550C5-425AXSP06	-	150.3	109.3	126.6	268.7	-	153.3	113.1	129.7	269	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK750C5-525AXSP06	-	170.5	-	144.4	302	-	174.6	129.5	148.1	303.3	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK750C5-425AXSP06	-	156.8	114.2	132.3	281.4	-	160.4	118.1	135.6	282.3	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK370K8-625AXSP08	-	156.8	118	134	265.7	-	158	120	135.3	264.2	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK370K8-525AXSP08	-	148.2	110.9	126.3	254.1	92.8	149.4	112.8	127.6	253.1	200	21	3"	160	13.9	3"	240	29.5	3"
EAW-FD15S2ZK370K8-425AXSP06	-	130.7	-	110.4	232.6	-	133.3	-	112.8	232.5	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK550K8-625AXSP08	-	172.6	129.8	147.5	293.5	-	174.3	132.1	149.2	292.6	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK550K8-525AXSP06	-	156.7	-	132.4	276.6	-	159.8	-	135.7	276.7	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK550K8-425AXSP06	-	143.5	104.6	121.1	256.6	-	146.4	108.1	124.1	256.6	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S2ZK750K8-625AXSP08	-	182.4	137.1	155.9	311.3	115.5	184.7	139.7	158	310.7	242	22.5	3"	194	14.8	3"	291	27.2	4"
EAW-FD15S2ZK750K8-525AXSP06	-	165.9	-	140.4	293.8	-	169.5	-	143.9	294.1	272	15.3	4"	218	12.6	3"	327	21.5	4"
EAW-FD15S2ZK750K8-425AXSP06	-	152.2	110.9	128.5	272.5	-	155.5	114.7	131.7	273.2	218	17.1	3"	174	11.3	3"	262	20.5	4"
EAW-FD15S3ZK370K4-625AXSP06	-	239.3	181.2	205.1	402.5	153	240.4	183.6	206.4	400.1	327	21.9	4"	262	14.5	4"	392	30.8	4"
EAW-FD15S3ZK370K4-525AXSP04	-	211.6	-	-	372.6	-	215.6	-	-	372.7	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK370K4-425AXSP04	-	194.7	-	164.2	347.3	-	198.5	-	168	347.2	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK550K4-625AXSP04	-	246.3	-	-	430.5	-	251.2	-	-	430.4	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK550K4-525AXSP04	-	232.4	-	196.6	410.8	-	237.4	-	201.5	411.1	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK550K4-425AXSP04	-	213.6	155.5	180.4	382.4	-	218.1	161	184.6	383.1	327	15.5	4"	262	10.2	4"	392	21.7	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3ZK750K4-625AXSP04	-	260.5	-	-	456.3	-	266.4	-	-	456.8	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK750K4-525AXSP04	-	246.4	-	208.4	436.4	-	251.9	-	213.7	437.4	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK750K4-425AXSP04	-	226.6	165	191.1	406.7	-	231.5	170.8	196.1	407.8	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK370K5-625AXSP06	-	239.3	181.2	205.1	402.5	153	240.4	183.6	206.4	400.1	327	21.9	4"	262	14.5	4"	392	30.8	4"
EAW-FD15S3ZK370K5-525AXSP04	-	211.6	-	-	372.6	-	215.6	-	-	372.7	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK370K5-425AXSP04	-	194.7	-	164.2	347.3	-	198.5	-	168	347.2	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK550K5-625AXSP04	-	246.3	-	-	430.5	-	251.2	-	-	430.4	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK550K5-525AXSP04	-	232.4	-	196.6	410.8	-	237.4	-	201.5	411.1	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK550K5-425AXSP04	-	213.6	155.5	180.4	382.4	-	218.1	161	184.6	383.1	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK750K5-625AXSP04	-	260.5	-	-	456.3	-	266.4	-	-	456.8	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK750K5-525AXSP04	-	246.4	-	208.4	436.4	-	251.9	-	213.7	437.4	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK750K5-425AXSP04	-	226.6	165	191.1	406.7	-	231.5	170.8	196.1	407.8	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK370C4-625AXSP06	152.40	245.1	185.8	210	412.6	157	247	188.5	212.2	411.3	327	21.9	4"	262	14.5	4"	392	30.8	4"
EAW-FD15S3ZK370C4-525AXSP04	-	218.1	-	-	384.6	-	222.6	-	188.9	384.8	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK370C4-425AXSP04	-	201	-	169.7	359.4	-	205.3	151.5	173.8	359.2	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK550C4-625AXSP04	-	257.2	-	-	450.3	-	263	-	-	451.3	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK550C4-525AXSP04	-	243.4	-	205.9	430.7	-	248.7	-	211.1	431.7	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK550C4-425AXSP04	-	223.7	162.7	188.5	400.4	-	228.3	168.3	193.2	401.6	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK750C4-525AXSP04	-	253.2	-	213.9	449.1	-	259	192.1	219.9	450.5	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK750C4-425AXSP04	-	233.4	169.9	197	419.2	-	238.7	175.9	202	420.7	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK370C5-625AXSP06	152.40	245.1	185.8	210	412.6	157	247	188.5	212.2	411.3	327	21.9	4"	262	14.5	4"	392	30.8	4"
EAW-FD15S3ZK370C5-525AXSP04	-	218.1	-	-	384.6	-	222.6	-	188.9	384.8	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK370C5-425AXSP04	-	201	-	169.7	359.4	-	205.3	151.5	173.8	359.2	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK550C5-625AXSP04	-	257.2	-	-	450.3	-	263	-	-	451.3	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK550C5-525AXSP04	-	243.4	-	205.9	430.7	-	248.7	-	211.1	431.7	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK550C5-425AXSP04	-	223.7	162.7	188.5	400.4	-	228.3	168.3	193.2	401.6	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK750C5-525AXSP04	-	253.2	-	213.9	449.1	-	259	192.1	219.9	450.5	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK750C5-425AXSP04	-	233.4	169.9	197	419.2	-	238.7	175.9	202	420.7	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK370K8-625AXSP06	-	239.3	181.2	205.1	402.5	153	240.4	183.6	206.4	400.1	327	21.9	4"	262	14.5	4"	392	30.8	4"
EAW-FD15S3ZK370K8-525AXSP04	-	211.6	-	-	372.6	-	215.6	-	-	372.7	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK370K8-425AXSP04	-	194.7	-	164.2	347.3	-	198.5	-	168	347.2	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK550K8-625AXSP04	-	246.3	-	-	430.5	-	251.2	-	-	430.4	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK550K8-525AXSP04	-	232.4	-	196.6	410.8	-	237.4	-	201.5	411.1	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK550K8-425AXSP04	-	213.6	155.5	180.4	382.4	-	218.1	161	184.6	383.1	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S3ZK750K8-625AXSP04	-	260.5	-	-	456.3	-	266.4	-	-	456.8	490	14.3	(2) 4"	392	12.3	4"	589	20.1	(2) 4"
EAW-FD15S3ZK750K8-525AXSP04	-	246.4	-	208.4	436.4	-	251.9	-	213.7	437.4	406	16.9	4"	325	11.1	4"	487	19.4	(2) 4"
EAW-FD15S3ZK750K8-425AXSP04	-	226.6	165	191.1	406.7	-	231.5	170.8	196.1	407.8	327	15.5	4"	262	10.2	4"	392	21.7	4"
EAW-FD15S4ZK370K4-625AXSP04	-	312.7	235.2	267.3	530.8	-	315.6	239.6	270.3	527.8	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK370K4-525AXSP04	-	295.9	221.4	252.2	508.3	-	298.8	225.2	255.3	506.2	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK370K4-425AXSP04	162.60	272.3	202.7	231.9	473.8	168.5	275.3	206.2	234.5	472.1	327	19.3	4"	262	12.7	4"	392	27.2	4"
EAW-FD15S4ZK550K4-625AXSP04	-	344.3	258.8	294.1	586.3	-	347.7	263.4	297.6	584.6	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK550K4-525AXSP04	195.70	325.1	243	277.4	560.9	203.3	328.6	247.4	280.4	559.5	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK550K4-425AXSP02	-	-	-	-	475.3	-	-	-	-	480.3	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750K4-625AXSP04	-	364.3	273.3	310.9	621.7	230.2	368.5	279	315.4	620.7	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK750K4-525AXSP02	-	-	-	-	546.7	-	-	-	-	552.8	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK750K4-425AXSP02	-	-	-	-	505.5	-	-	-	-	511.1	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370K5-625AXSP04	-	312.7	235.2	267.3	530.8	-	315.6	239.6	270.3	527.8	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK370K5-525AXSP04	-	295.9	221.4	252.2	508.3	-	298.8	225.2	255.3	506.2	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK370K5-425AXSP04	162.60	272.3	202.7	231.9	473.8	168.5	275.3	206.2	234.5	472.1	327	19.3	4"	262	12.7	4"	392	27.2	4"
EAW-FD15S4ZK550K5-625AXSP04	-	344.3	258.8	294.1	586.3	-	347.7	263.4	297.6	584.6	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK550K5-525AXSP04	195.70	325.1	243	277.4	560.9	203.3	328.6	247.4	280.4	559.5	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK550K5-425AXSP02	-	-	-	-	475.3	-	-	-	-	480.3	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750K5-625AXSP04	-	364.3	273.3	310.9	621.7	230.2	368.5	279	315.4	620.7	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK750K5-525AXSP02	-	-	-	-	546.7	-	-	-	-	552.8	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK750K5-425AXSP02	-	-	-	-	505.5	-	-	-	-	511.1	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370C4-625AXSP04	-	320.3	241.1	274	544.2	-	324.1	245.9	277.4	543.2	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK370C4-525AXSP04	-	305.1	228.1	259.9	524.8	191	308.2	232.4	263.1	522.8	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK370C4-425AXSP02	-	-	-	-	446.9	-	-	-	-	451.8	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK550C4-625AXSP04	-	359.7	270	307	613.6	227.4	363.7	275.5	311.4	612.4	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK550C4-525AXSP02	-	-	-	-	539.8	-	-	-	-	545.7	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK550C4-425AXSP02	-	-	-	-	497.8	-	-	-	-	503.6	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750C4-525AXSP02	-	-	-	-	562.3	-	-	-	-	569.8	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK750C4-425AXSP02	-	-	-	-	520.5	-	-	-	-	527.7	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370C5-625AXSP04	-	320.3	241.1	274	544.2	-	324.1	245.9	277.4	543.2	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK370C5-525AXSP04	-	305.1	228.1	259.9	524.8	191	308.2	232.4	263.1	522.8	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK370C5-425AXSP02	-	-	-	-	446.9	-	-	-	-	451.8	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK550C5-625AXSP04	-	359.7	270	307	613.6	227.4	363.7	275.5	311.4	612.4	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK550C5-525AXSP02	-	-	-	-	539.8	-	-	-	-	545.7	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK550C5-425AXSP02	-	-	-	-	497.8	-	-	-	-	503.6	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750C5-525AXSP02	-	-	-	-	562.3	-	-	-	-	569.8	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK750C5-425AXSP02	-	-	-	-	520.5	-	-	-	-	527.7	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370K8-625AXSP04	-	312.7	235.2	267.3	530.8	-	315.6	239.6	270.3	527.8	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK370K8-525AXSP04	-	295.9	221.4	252.2	508.3	-	298.8	225.2	255.3	506.2	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK370K8-425AXSP04	162.60	272.3	202.7	231.9	473.8	168.5	275.3	206.2	234.5	472.1	327	19.3	4"	262	12.7	4"	392	27.2	4"
EAW-FD15S4ZK550K8-625AXSP04	-	344.3	258.8	294.1	586.3	-	347.7	263.4	297.6	584.6	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK550K8-525AXSP04	195.70	325.1	243	277.4	560.9	203.3	328.6	247.4	280.4	559.5	406	20.7	4"	325	13.7	4"	487	24.8	(2) 4"
EAW-FD15S4ZK550K8-425AXSP02	-	-	-	-	475.3	-	-	-	-	480.3	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750K8-625AXSP04	-	364.3	273.3	310.9	621.7	230.2	368.5	279	315.4	620.7	490	18.2	(2) 4"	392	14.9	4"	589	25.5	(2) 4"
EAW-FD15S4ZK750K8-525AXSP02	-	-	-	-	546.7	-	-	-	-	552.8	818	12.4	(2) 4"	654	8.2	(2) 4"	981	14.3	(3) 4"
EAW-FD15S4ZK750K8-425AXSP02	-	-	-	-	505.5	-	-	-	-	511.1	654	11	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S5ZK370K4-625AXSP02	-	-	-	-	629	-	-	-	-	630.6	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370K4-525AXSP02	-	-	-	-	602.4	-	-	-	-	604.6	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK370K4-425AXSP02	-	303.9	-	-	557.3	-	313.5	-	-	559.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550K4-625AXSP02	-	-	-	-	694.7	-	-	-	-	696.7	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550K4-525AXSP02	-	-	-	-	663.5	-	-	-	-	667.3	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK550K4-425AXSP02	-	333.5	-	-	613.6	-	344.2	-	-	616.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750K4-625AXSP02	-	-	-	-	735.9	-	-	-	-	740.1	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK750K4-525AXSP02	-	386.6	-	-	704.3	-	399.5	-	-	708.5	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK750K4-425AXSP02	-	353.5	-	-	651	-	365.6	-	307	655.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370K5-625AXSP02	-	-	-	-	629	-	-	-	-	630.6	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370K5-525AXSP02	-	-	-	-	602.4	-	-	-	-	604.6	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK370K5-425AXSP02	-	303.9	-	-	557.3	-	313.5	-	-	559.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550K5-625AXSP02	-	-	-	-	694.7	-	-	-	-	696.7	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550K5-525AXSP02	-	-	-	-	663.5	-	-	-	-	667.3	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK550K5-425AXSP02	-	333.5	-	-	613.6	-	344.2	-	-	616.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750K5-625AXSP02	-	-	-	-	735.9	-	-	-	-	740.1	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK750K5-525AXSP02	-	386.6	-	-	704.3	-	399.5	-	-	708.5	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK750K5-425AXSP02	-	353.5	-	-	651	-	365.6	-	307	655.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370C4-625AXSP02	-	-	-	-	645.4	-	-	-	-	648	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370C4-525AXSP02	-	-	-	-	620.7	-	-	-	-	624.1	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK370C4-425AXSP02	-	314	-	-	576.5	-	323.9	-	-	579.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S5ZK550C4-625AXSP02	-	-	-	-	726.4	-	-	-	-	730.3	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550C4-525AXSP02	-	382	-	-	695.3	-	394.6	-	-	699.3	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK550C4-425AXSP02	-	348.8	-	-	642	-	360.6	-	302.7	645.7	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750C4-525AXSP02	-	397.6	-	-	724.6	-	411.2	-	-	730.5	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK750C4-425AXSP02	-	364.4	-	304.7	671.7	-	376.5	-	316.5	676.9	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370C5-625AXSP02	-	-	-	-	645.4	-	-	-	-	648	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370C5-525AXSP02	-	-	-	-	620.7	-	-	-	-	624.1	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK370C5-425AXSP02	-	314	-	-	576.5	-	323.9	-	-	579.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550C5-625AXSP02	-	-	-	-	726.4	-	-	-	-	730.3	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550C5-525AXSP02	-	382	-	-	695.3	-	394.6	-	-	699.3	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK550C5-425AXSP02	-	348.8	-	-	642	-	360.6	-	302.7	645.7	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750C5-525AXSP02	-	397.6	-	-	724.6	-	411.2	-	-	730.5	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK750C5-425AXSP02	-	364.4	-	304.7	671.7	-	376.5	-	316.5	676.9	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370K8-625AXSP02	-	-	-	-	629	-	-	-	-	630.6	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370K8-525AXSP02	-	-	-	-	602.4	-	-	-	-	604.6	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK370K8-425AXSP02	-	303.9	-	-	557.3	-	313.5	-	-	559.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550K8-625AXSP02	-	-	-	-	694.7	-	-	-	-	696.7	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550K8-525AXSP02	-	-	-	-	663.5	-	-	-	-	667.3	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK550K8-425AXSP02	-	333.5	-	-	613.6	-	344.2	-	-	616.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750K8-625AXSP02	-	-	-	-	735.9	-	-	-	-	740.1	981	12.9	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK750K8-525AXSP02	-	386.6	-	-	704.3	-	399.5	-	-	708.5	818	14.4	(2) 4"	654	9.4	(2) 4"	981	17	(3) 4"
EAW-FD15S5ZK750K8-425AXSP02	-	353.5	-	-	651	-	365.6	-	307	655.4	654	12.9	(2) 4"	523	8.5	(2) 4"	785	18.1	(2) 4"
EAW-FD15S6ZK370K4-625AXSP02	-	-	-	-	769.3	-	-	-	-	768.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK370K4-525AXSP02	-	416.5	-	-	737	-	425.3	-	-	736.4	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK370K4-425AXSP02	-	380.9	-	321.2	681.7	-	388.7	-	329.1	682.9	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK550K4-625AXSP02	-	483.3	-	-	848.9	-	493.9	-	-	848.9	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK550K4-525AXSP02	-	457.2	-	386.2	812.4	-	467.4	-	396.8	813.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK550K4-425AXSP02	-	418.3	303.6	352.2	751.2	-	427.4	314.6	361.5	753	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK750K4-625AXSP02	-	511.6	-	-	899.6	-	523.7	-	-	902.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK750K4-525AXSP02	-	484.6	-	409.3	862.7	-	495.7	-	420	865	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK750K4-425AXSP02	-	443.4	321.8	373.3	797.3	-	453.5	333.5	383.5	801.1	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK370K5-625AXSP02	-	-	-	-	769.3	-	-	-	-	768.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK370K5-525AXSP02	-	416.5	-	-	737	-	425.3	-	-	736.4	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK370K5-425AXSP02	-	380.9	-	321.2	681.7	-	388.7	-	329.1	682.9	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK550K5-625AXSP02	-	483.3	-	-	848.9	-	493.9	-	-	848.9	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK550K5-525AXSP02	-	457.2	-	386.2	812.4	-	467.4	-	396.8	813.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK550K5-425AXSP02	-	418.3	303.6	352.2	751.2	-	427.4	314.6	361.5	753	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK750K5-625AXSP02	-	511.6	-	-	899.6	-	523.7	-	-	902.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK750K5-525AXSP02	-	484.6	-	409.3	862.7	-	495.7	-	420	865	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK750K5-425AXSP02	-	443.4	321.8	373.3	797.3	-	453.5	333.5	383.5	801.1	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK370C4-625AXSP02	-	-	-	-	788.4	-	460.4	-	-	789.3	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK370C4-525AXSP02	-	429.2	-	-	759.7	-	438.4	-	-	760.3	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK370C4-425AXSP02	-	393.8	-	331.7	705.3	-	402.5	-	340.4	706.3	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK550C4-625AXSP02	-	505.3	-	-	887.9	-	517	-	-	890.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK550C4-525AXSP02	-	478.7	-	404.5	851.6	-	490.3	-	414.9	853.7	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK550C4-425AXSP02	-	437	317.4	368.4	786.3	-	447.2	328.8	377.9	789	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK750C4-525AXSP02	-	497.8	-	420.8	886.5	-	510.4	-	432.1	890.7	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK750C4-425AXSP02	-	456.8	331.2	384.6	822.9	-	467.5	343.7	395.2	826.1	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK370C5-625AXSP02	-	-	-	-	788.4	-	460.4	-	-	789.3	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK370C5-525AXSP02	-	429.2	-	-	759.7	-	438.4	-	-	760.3	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK370C5-425AXSP02	-	393.8	-	331.7	705.3	-	402.5	-	340.4	706.3	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK550C5-625AXSP02	-	505.3	-	-	887.9	-	517	-	-	890.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK550C5-525AXSP02	-	478.7	-	404.5	851.6	-	490.3	-	414.9	853.7	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK550C5-425AXSP02	-	437	317.4	368.4	786.3	-	447.2	328.8	377.9	789	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK750C5-525AXSP02	-	497.8	-	420.8	886.5	-	510.4	-	432.1	890.7	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK750C5-425AXSP02	-	456.8	331.2	384.6	822.9	-	467.5	343.7	395.2	826.1	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK370K8-625AXSP02	-	-	-	-	769.3	-	-	-	-	768.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK370K8-525AXSP02	-	416.5	-	-	737	-	425.3	-	-	736.4	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK370K8-425AXSP02	-	380.9	-	321.2	681.7	-	388.7	-	329.1	682.9	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK550K8-625AXSP02	-	483.3	-	-	848.9	-	493.9	-	-	848.9	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK550K8-525AXSP02	-	457.2	-	386.2	812.4	-	467.4	-	396.8	813.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK550K8-425AXSP02	-	418.3	303.6	352.2	751.2	-	427.4	314.6	361.5	753	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S6ZK750K8-625AXSP02	-	511.6	-	-	899.6	-	523.7	-	-	902.1	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.9	(3) 4"
EAW-FD15S6ZK750K8-525AXSP02	-	484.6	-	409.3	862.7	-	495.7	-	420	865	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.7	(3) 4"
EAW-FD15S6ZK750K8-425AXSP02	-	443.4	321.8	373.3	797.3	-	453.5	333.5	383.5	801.1	654	14.8	(2) 4"	523	9.8	(2) 4"	785	20.9	(2) 4"
EAW-FD15S1PB370K4-625AXSP16	-	67.3	-	57.4	115.1	-	68.1	51.5	58.3	114.9	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB370K4-525AXSP16	-	64.2	47.7	54.7	111.2	-	65.1	48.9	55.5	111	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB370K4-425AXSP12	-	55.9	-	47	101	-	57.4	-	48.4	101.3	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB550K4-625AXSP16	-	73.4	54.8	62.5	125.9	-	74.4	56.1	63.6	125.9	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB550K4-525AXSP16	-	69.9	51.9	59.5	121.5	43.5	71	53.2	60.5	121.6	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB550K4-425AXSP12	-	60.8	-	51.2	110.2	-	62.5	45.8	52.8	110.8	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB750K4-625AXSP16	-	76.8	57.3	65.4	132	-	78	58.8	66.7	132.2	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB750K4-525AXSP12	-	69.4	-	58.5	124.2	-	71.4	-	60.3	124.9	121	15.3	3"	97	13.1	2"	145	21.5	3"
EAW-FD15S1PB750K4-425AXSP12	-	64.1	46.2	53.8	116.2	-	65.8	48.2	55.6	116.9	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB370K5-625AXSP16	-	67.3	-	57.4	115.1	-	68.1	51.5	58.3	114.9	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB370K5-525AXSP16	-	64.2	47.7	54.7	111.2	-	65.1	48.9	55.5	111	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB370K5-425AXSP12	-	55.9	-	47	101	-	57.4	-	48.4	101.3	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB550K5-625AXSP16	-	73.4	54.8	62.5	125.9	-	74.4	56.1	63.6	125.9	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB550K5-525AXSP16	-	69.9	51.9	59.5	121.5	43.5	71	53.2	60.5	121.6	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB550K5-425AXSP12	-	60.8	-	51.2	110.2	-	62.5	45.8	52.8	110.8	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB750K5-625AXSP16	-	76.8	57.3	65.4	132	-	78	58.8	66.7	132.2	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB750K5-525AXSP12	-	69.4	-	58.5	124.2	-	71.4	-	60.3	124.9	121	15.3	3"	97	13.1	2"	145	21.5	3"
EAW-FD15S1PB750K5-425AXSP12	-	64.1	46.2	53.8	116.2	-	65.8	48.2	55.6	116.9	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB370C4-625AXSP16	-	67.4	50.5	57.5	115.4	-	68.6	51.8	58.6	115.7	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB370C4-525AXSP16	-	65	48.4	55.3	112.8	-	66.1	49.6	56.4	112.8	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB370C4-425AXSP12	-	57.2	-	48.1	103.4	-	58.8	-	49.7	103.8	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB550C4-525AXSP12	-	68.5	-	57.7	122.6	-	70.5	-	59.6	123.4	121	15.3	3"	97	13.1	2"	145	21.5	3"
EAW-FD15S1PB550C4-425AXSP12	-	63.3	45.7	53.2	114.8	-	65.2	47.7	55	115.5	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB370C5-625AXSP16	-	67.4	50.5	57.5	115.4	-	68.6	51.8	58.6	115.7	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB370C5-525AXSP16	-	65	48.4	55.3	112.8	-	66.1	49.6	56.4	112.8	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB370C5-425AXSP12	-	57.2	-	48.1	103.4	-	58.8	-	49.7	103.8	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB550C5-525AXSP12	-	68.5	-	57.7	122.6	-	70.5	-	59.6	123.4	121	15.3	3"	97	13.1	2"	145	21.5	3"
EAW-FD15S1PB550C5-425AXSP12	-	63.3	45.7	53.2	114.8	-	65.2	47.7	55	115.5	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB370K8-625AXSP16	-	67.3	-	57.4	115.1	-	68.1	51.5	58.3	114.9	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB370K8-525AXSP16	-	64.2	47.7	54.7	111.2	-	65.1	48.9	55.5	111	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB370K8-425AXSP12	-	55.9	-	47	101	-	57.4	-	48.4	101.3	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB550K8-625AXSP16	-	73.4	54.8	62.5	125.9	-	74.4	56.1	63.6	125.9	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB550K8-525AXSP16	-	69.9	51.9	59.5	121.5	43.5	71	53.2	60.5	121.6	91	22.2	2"	73	14.7	2"	109	31.2	2"
EAW-FD15S1PB550K8-425AXSP12	-	60.8	-	51.2	110.2	-	62.5	45.8	52.8	110.8	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S1PB750K8-625AXSP16	-	76.8	57.3	65.4	132	-	78	58.8	66.7	132.2	109	23.7	2"	87	15.6	2"	131	27.8	3"
EAW-FD15S1PB750K8-525AXSP12	-	69.4	-	58.5	124.2	-	71.4	-	60.3	124.9	121	15.3	3"	97	13.1	2"	145	21.5	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1PB750K8-425AXSP12	-	64.1	46.2	53.8	116.2	-	65.8	48.2	55.6	116.9	97	17.9	2"	78	11.8	2"	116	25.2	2"
EAW-FD15S2PB370K4-625AXSP08	-	134	-	114.3	229.4	-	135.9	102.5	116.2	229	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB370K4-525AXSP08	-	127.9	95	108.8	221.7	-	129.6	97.3	110.5	221.5	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB370K4-425AXSP06	-	111	-	93.4	200.6	-	113.9	-	96.2	201.3	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB550K4-625AXSP08	-	146.1	109.1	124.4	250.9	-	148.2	111.8	126.7	250.8	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB550K4-525AXSP08	-	139.2	103.3	118.3	242.1	86.4	141.4	105.9	120.5	242.2	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB550K4-425AXSP06	-	121	-	101.6	219	-	124.3	90.9	104.8	220.1	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB750K4-625AXSP08	-	152.9	114	130.2	263.1	-	155.2	117.1	132.7	263.5	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB750K4-525AXSP06	-	137.6	-	116.1	247.3	-	141.8	-	119.8	248.7	242	16.7	3"	194	11	3"	291	19.3	4"
EAW-FD15S2PB750K4-425AXSP06	-	127.1	91.5	106.8	230.7	-	130.8	95.7	110.3	232.3	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB370K5-625AXSP08	-	134	-	114.3	229.4	-	135.9	102.5	116.2	229	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB370K5-525AXSP08	-	127.9	95	108.8	221.7	-	129.6	97.3	110.5	221.5	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB370K5-425AXSP06	-	111	-	93.4	200.6	-	113.9	-	96.2	201.3	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB550K5-625AXSP08	-	146.1	109.1	124.4	250.9	-	148.2	111.8	126.7	250.8	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB550K5-525AXSP08	-	139.2	103.3	118.3	242.1	86.4	141.4	105.9	120.5	242.2	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB550K5-425AXSP06	-	121	-	101.6	219	-	124.3	90.9	104.8	220.1	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB750K5-625AXSP08	-	152.9	114	130.2	263.1	-	155.2	117.1	132.7	263.5	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB750K5-525AXSP06	-	137.6	-	116.1	247.3	-	141.8	-	119.8	248.7	242	16.7	3"	194	11	3"	291	19.3	4"
EAW-FD15S2PB750K5-425AXSP06	-	127.1	91.5	106.8	230.7	-	130.8	95.7	110.3	232.3	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB370C4-625AXSP08	-	134.3	-	114.5	230.2	-	136.6	103.2	116.7	230.5	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB370C4-525AXSP08	-	129.5	96.2	110.2	224.6	-	131.6	98.8	112.2	225.1	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB370C4-425AXSP06	-	113.5	-	95.4	205.4	-	116.8	-	98.5	206.7	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB550C4-525AXSP06	-	136.1	-	114.6	243.8	-	140	-	118.3	245.5	242	16.7	3"	194	11	3"	291	19.3	4"
EAW-FD15S2PB550C4-425AXSP06	-	125.7	90.5	105.6	228	-	129.3	94.6	109	229.8	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB370C5-625AXSP08	-	134.3	-	114.5	230.2	-	136.6	103.2	116.7	230.5	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB370C5-525AXSP08	-	129.5	96.2	110.2	224.6	-	131.6	98.8	112.2	225.1	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB370C5-425AXSP06	-	113.5	-	95.4	205.4	-	116.8	-	98.5	206.7	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB550C5-525AXSP06	-	136.1	-	114.6	243.8	-	140	-	118.3	245.5	242	16.7	3"	194	11	3"	291	19.3	4"
EAW-FD15S2PB550C5-425AXSP06	-	125.7	90.5	105.6	228	-	129.3	94.6	109	229.8	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB370K8-625AXSP08	-	134	-	114.3	229.4	-	135.9	102.5	116.2	229	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB370K8-525AXSP08	-	127.9	95	108.8	221.7	-	129.6	97.3	110.5	221.5	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB370K8-425AXSP06	-	111	-	93.4	200.6	-	113.9	-	96.2	201.3	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB550K8-625AXSP08	-	146.1	109.1	124.4	250.9	-	148.2	111.8	126.7	250.8	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB550K8-525AXSP08	-	139.2	103.3	118.3	242.1	86.4	141.4	105.9	120.5	242.2	182	18.9	3"	145	12.5	3"	218	26.6	3"
EAW-FD15S2PB550K8-425AXSP06	-	121	-	101.6	219	-	124.3	90.9	104.8	220.1	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S2PB750K8-625AXSP08	-	152.9	114	130.2	263.1	-	155.2	117.1	132.7	263.5	218	20	3"	174	13.2	3"	262	24.6	4"
EAW-FD15S2PB750K8-525AXSP06	-	137.6	-	116.1	247.3	-	141.8	-	119.8	248.7	242	16.7	3"	194	11	3"	291	19.3	4"
EAW-FD15S2PB750K8-425AXSP06	-	127.1	91.5	106.8	230.7	-	130.8	95.7	110.3	232.3	194	15.1	3"	155	10	3"	232	21.3	3"
EAW-FD15S3PB370K4-625AXSP06	-	203.9	153.5	174.3	346.2	-	206.1	156.1	176.3	345.2	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB370K4-525AXSP04	-	179.6	-	-	321.7	-	184.7	-	-	322.4	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB370K4-425AXSP04	-	165.2	-	138.9	299	-	169.6	-	143.2	300.5	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB550K4-625AXSP06	135.40	222.3	166.8	189.7	378.7	140.6	224.8	170.3	192.3	378.1	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB550K4-525AXSP04	-	195.7	-	-	350.9	-	201.2	-	170.2	352.8	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB550K4-425AXSP04	-	179.9	-	151.1	326.8	-	185	135.2	155.9	328	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB750K4-625AXSP04	-	215.4	-	-	382.4	-	221.3	-	-	384.2	436	16.3	4"	349	10.7	4"	523	18	(2) 4"
EAW-FD15S3PB750K4-525AXSP04	-	205	-	172.8	368.7	-	211.3	-	178.4	370.9	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB750K4-425AXSP04	-	189.1	136.1	158.9	343.7	-	194.7	142.3	164.2	346.6	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB370K5-625AXSP06	-	203.9	153.5	174.3	346.2	-	206.1	156.1	176.3	345.2	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB370K5-525AXSP04	-	179.6	-	-	321.7	-	184.7	-	-	322.4	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB370K5-425AXSP04	-	165.2	-	138.9	299	-	169.6	-	143.2	300.5	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB550K5-625AXSP06	135.40	222.3	166.8	189.7	378.7	140.6	224.8	170.3	192.3	378.1	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB550K5-525AXSP04	-	195.7	-	-	350.9	-	201.2	-	170.2	352.8	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB550K5-425AXSP04	-	179.9	-	151.1	326.8	-	185	135.2	155.9	328	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB750K5-625AXSP04	-	215.4	-	-	382.4	-	221.3	-	-	384.2	436	16.3	4"	349	10.7	4"	523	18	(2) 4"
EAW-FD15S3PB750K5-525AXSP04	-	205	-	172.8	368.7	-	211.3	-	178.4	370.9	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB750K5-425AXSP04	-	189.1	136.1	158.9	343.7	-	194.7	142.3	164.2	346.6	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB370C4-625AXSP06	-	204.3	153.8	174.6	347	-	207.1	157.1	177.4	347.4	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB370C4-525AXSP04	-	182	-	-	325.8	-	187.6	-	-	327.6	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB370C4-425AXSP04	-	168.9	-	142.1	306.1	-	173.9	-	146.8	308	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB550C4-525AXSP04	-	202.7	-	170.6	363.6	-	208.7	-	176.2	366.1	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB550C4-425AXSP04	-	187	134.6	157.1	340.2	-	192.5	140.7	162.3	342.4	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB370C5-625AXSP06	-	204.3	153.8	174.6	347	-	207.1	157.1	177.4	347.4	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB370C5-525AXSP04	-	182	-	-	325.8	-	187.6	-	-	327.6	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB370C5-425AXSP04	-	168.9	-	142.1	306.1	-	173.9	-	146.8	308	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB550C5-525AXSP04	-	202.7	-	170.6	363.6	-	208.7	-	176.2	366.1	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB550C5-425AXSP04	-	187	134.6	157.1	340.2	-	192.5	140.7	162.3	342.4	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB370K8-625AXSP06	-	203.9	153.5	174.3	346.2	-	206.1	156.1	176.3	345.2	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB370K8-525AXSP04	-	179.6	-	-	321.7	-	184.7	-	-	322.4	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB370K8-425AXSP04	-	165.2	-	138.9	299	-	169.6	-	143.2	300.5	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB550K8-625AXSP06	135.40	222.3	166.8	189.7	378.7	140.6	224.8	170.3	192.3	378.1	291	19.6	4"	232	15.7	3"	349	27.5	4"
EAW-FD15S3PB550K8-525AXSP04	-	195.7	-	-	350.9	-	201.2	-	170.2	352.8	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB550K8-425AXSP04	-	179.9	-	151.1	326.8	-	185	135.2	155.9	328	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S3PB750K8-625AXSP04	-	215.4	-	-	382.4	-	221.3	-	-	384.2	436	16.3	4"	349	10.7	4"	523	18	(2) 4"
EAW-FD15S3PB750K8-525AXSP04	-	205	-	172.8	368.7	-	211.3	-	178.4	370.9	363	14.9	4"	291	9.8	4"	436	20.9	4"
EAW-FD15S3PB750K8-425AXSP04	-	189.1	136.1	158.9	343.7	-	194.7	142.3	164.2	346.6	291	13.7	4"	232	11.8	3"	349	19.3	4"
EAW-FD15S4PB370K4-625AXSP04	-	265.8	-	226.6	456	-	269.6	203.2	230.3	455.2	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB370K4-525AXSP04	-	253.4	188	215.4	439.8	-	256.9	192.7	219.2	439.4	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB370K4-425AXSP04	136.50	233.1	172	197.7	409.6	142.9	236.6	176.1	200.8	409.5	291	17.2	4"	232	14.1	3"	349	24.2	4"
EAW-FD15S4PB550K4-625AXSP04	-	289.7	216.1	246.8	498.5	-	294	221.6	251.1	498.6	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB550K4-525AXSP04	-	275.7	204.7	234.2	480.7	170.9	280.2	209.6	238.5	481.1	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB550K4-425AXSP02	-	-	-	-	402.7	-	-	-	-	409.2	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB750K4-625AXSP04	-	303.2	225.7	258.1	522.8	-	308.3	231.9	263	523.6	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB750K4-525AXSP04	170.60	289.2	214.1	245.7	504.7	178.9	294	219.8	250.3	506.1	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB750K4-425AXSP02	-	-	-	-	424.2	-	-	-	-	431.7	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370K5-625AXSP04	-	265.8	-	226.6	456	-	269.6	203.2	230.3	455.2	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB370K5-525AXSP04	-	253.4	188	215.4	439.8	-	256.9	192.7	219.2	439.4	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB370K5-425AXSP04	136.50	233.1	172	197.7	409.6	142.9	236.6	176.1	200.8	409.5	291	17.2	4"	232	14.1	3"	349	24.2	4"
EAW-FD15S4PB550K5-625AXSP04	-	289.7	216.1	246.8	498.5	-	294	221.6	251.1	498.6	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB550K5-525AXSP04	-	275.7	204.7	234.2	480.7	170.9	280.2	209.6	238.5	481.1	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB550K5-425AXSP02	-	-	-	-	402.7	-	-	-	-	409.2	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB750K5-625AXSP04	-	303.2	225.7	258.1	522.8	-	308.3	231.9	263	523.6	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB750K5-525AXSP04	170.60	289.2	214.1	245.7	504.7	178.9	294	219.8	250.3	506.1	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB750K5-425AXSP02	-	-	-	-	424.2	-	-	-	-	431.7	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370C4-625AXSP04	-	266.4	-	227	456.9	-	271.3	204.5	231.7	458.1	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB370C4-525AXSP04	-	256.5	190.4	218.3	446.1	-	260.9	195.8	222.5	446.5	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB370C4-425AXSP02	-	-	-	-	378.1	-	-	-	-	384.4	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB550C4-525AXSP04	168.60	285.3	211.8	242.5	497.7	176.8	290.7	217.5	247.3	499.4	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB550C4-425AXSP02	-	-	-	-	419.4	-	-	-	-	426.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370C5-625AXSP04	-	266.4	-	227	456.9	-	271.3	204.5	231.7	458.1	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB370C5-525AXSP04	-	256.5	190.4	218.3	446.1	-	260.9	195.8	222.5	446.5	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB370C5-425AXSP02	-	-	-	-	378.1	-	-	-	-	384.4	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S4PB550C5-525AXSP04	168.60	285.3	211.8	242.5	497.7	176.8	290.7	217.5	247.3	499.4	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB550C5-425AXSP02	-	-	-	-	419.4	-	-	-	-	426.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370K8-625AXSP04	-	265.8	-	226.6	456	-	269.6	203.2	230.3	455.2	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB370K8-525AXSP04	-	253.4	188	215.4	439.8	-	256.9	192.7	219.2	439.4	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB370K8-425AXSP04	136.50	233.1	172	197.7	409.6	142.9	236.6	176.1	200.8	409.5	291	17.2	4"	232	14.1	3"	349	24.2	4"
EAW-FD15S4PB550K8-625AXSP04	-	289.7	216.1	246.8	498.5	-	294	221.6	251.1	498.6	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB550K8-525AXSP04	-	275.7	204.7	234.2	480.7	170.9	280.2	209.6	238.5	481.1	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB550K8-425AXSP02	-	-	-	-	402.7	-	-	-	-	409.2	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB750K8-625AXSP04	-	303.2	225.7	258.1	522.8	-	308.3	231.9	263	523.6	436	19.8	4"	349	13	4"	523	22.9	(2) 4"
EAW-FD15S4PB750K8-525AXSP04	170.60	289.2	214.1	245.7	504.7	178.9	294	219.8	250.3	506.1	363	18.4	4"	291	12.1	4"	436	25.8	4"
EAW-FD15S4PB750K8-425AXSP02	-	-	-	-	424.2	-	-	-	-	431.7	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S5PB370K4-625AXSP04	211.90	342.6	259	293.1	578.5	218.5	345.3	262.6	295.9	576	436	23.2	4"	349	15.3	4"	523	27.7	(2) 4"
EAW-FD15S5PB370K4-525AXSP02	-	-	-	-	515.8	-	-	-	-	520.3	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370K4-425AXSP02	-	-	-	-	478.9	-	-	-	-	482.5	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB550K4-625AXSP02	-	-	-	-	586.6	-	-	-	-	591.9	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	16	(3) 4"
EAW-FD15S5PB550K4-525AXSP02	-	-	-	-	562.6	-	-	-	-	567.9	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550K4-425AXSP02	-	278.4	-	-	521.7	-	290.1	-	-	526.9	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB750K4-625AXSP02	-	-	-	-	614.5	-	-	-	-	620.4	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	16	(3) 4"
EAW-FD15S5PB750K4-525AXSP02	-	-	-	-	590.9	-	-	-	-	596.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB750K4-425AXSP02	-	292.6	-	-	549.1	-	305.4	-	-	555.3	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB370K5-625AXSP04	211.90	342.6	259	293.1	578.5	218.5	345.3	262.6	295.9	576	436	23.2	4"	349	15.3	4"	523	27.7	(2) 4"
EAW-FD15S5PB370K5-525AXSP02	-	-	-	-	515.8	-	-	-	-	520.3	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370K5-425AXSP02	-	-	-	-	478.9	-	-	-	-	482.5	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB550K5-625AXSP02	-	-	-	-	586.6	-	-	-	-	591.9	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	16	(3) 4"
EAW-FD15S5PB550K5-525AXSP02	-	-	-	-	562.6	-	-	-	-	567.9	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550K5-425AXSP02	-	278.4	-	-	521.7	-	290.1	-	-	526.9	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB750K5-625AXSP02	-	-	-	-	614.5	-	-	-	-	620.4	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	16	(3) 4"
EAW-FD15S5PB750K5-525AXSP02	-	-	-	-	590.9	-	-	-	-	596.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB750K5-425AXSP02	-	292.6	-	-	549.1	-	305.4	-	-	555.3	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB370C4-625AXSP04	212.60	343.3	259.5	294.1	579.7	219.8	347	264.2	297.7	579.7	436	23.2	4"	349	15.3	4"	523	27.7	(2) 4"
EAW-FD15S5PB370C4-525AXSP02	-	-	-	-	523.1	-	-	-	-	528.6	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370C4-425AXSP02	-	-	-	-	489.3	-	273.1	-	-	494.5	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB550C4-525AXSP02	-	-	-	-	582.8	-	-	-	-	589.8	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550C4-425AXSP02	-	289.2	-	-	542.7	-	301.8	-	-	549.6	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB370K5-625AXSP04	212.60	343.3	259.5	294.1	579.7	219.8	347	264.2	297.7	579.7	436	23.2	4"	349	15.3	4"	523	27.7	(2) 4"
EAW-FD15S5PB370C5-525AXSP02	-	-	-	-	523.1	-	-	-	-	528.6	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370C5-425AXSP02	-	-	-	-	489.3	-	273.1	-	-	494.5	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB550C5-525AXSP02	-	-	-	-	582.8	-	-	-	-	589.8	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550C5-425AXSP02	-	289.2	-	-	542.7	-	301.8	-	-	549.6	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB370K8-625AXSP04	211.90	342.6	259	293.1	578.5	218.5	345.3	262.6	295.9	576	436	23.2	4"	349	15.3	4"	523	27.7	(2) 4"
EAW-FD15S5PB370K8-525AXSP02	-	-	-	-	515.8	-	-	-	-	520.3	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370K8-425AXSP02	-	-	-	-	478.9	-	-	-	-	482.5	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB550K8-625AXSP02	-	-	-	-	586.6	-	-	-	-	591.9	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	16	(3) 4"
EAW-FD15S5PB550K8-525AXSP02	-	-	-	-	562.6	-	-	-	-	567.9	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550K8-425AXSP02	-	278.4	-	-	521.7	-	290.1	-	-	526.9	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-FD15S5PB750K8-625AXSP02	-	-	-	-	614.5	-	-	-	-	620.4	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	16	(3) 4"
EAW-FD15S5PB750K8-525AXSP02	-	-	-	-	590.9	-	-	-	-	596.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB750K8-425AXSP02	-	292.6	-	-	549.1	-	305.4	-	-	555.3	581	11.3	(2) 4"	465	7.5	(2) 4"	698	16	(2) 4"
EAW-DD1504XL017G7-625AXSP08	-	624.4	468.7	533.6	1068.1	-	627.9	474.5	536.9	1058.3	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD1504XL017G7-525AXSP06	-	547.8	-	463.6	972.2	-	556.6	-	471.7	966.8	952	15.4	4"	762	10.2	4"	1143	21.7	4"
EAW-DD1508XL017G7-625AXSP04	-	1243.4	931.2	1060.6	2127.9	-	1248.7	944.6	1067.4	2111.3	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD1508XL017G7-525AXSP04	684.80	1144	851.9	973	1978.3	707.2	1149.5	864.1	979.9	1964	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD1512XL017G7-625AXSP02	-	1742.9	-	-	3076.3	-	1772.3	-	-	3062.2	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD1512XL017G7-525AXSP02	-	1604.2	-	1352.4	2857	-	1631.6	-	1380.4	2846.6	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S1XL045M4-621AXSP08	-	589.2	443.4	503.3	1000	-	591.9	448.9	506.6	990.8	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL045M4-621AXSP04	-	1173.6	881.3	1002.2	1995	-	1177.5	893.8	1008.9	1976.9	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL045M4-621AXSP04	1172.50	1837.6	1405.3	1580.2	-	1184.4	1829.9	1406.3	1575.6	-	1722	25.5	6"	1377	20.3	4"	2066	35.7	6"
EAW-DD33S1XL045M4-525AXSP08	-	542.2	405.3	461.8	934.1	336.7	544.8	410.3	465.1	926.5	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL045M4-625AXSP08	-	587.9	441.6	502	1001.8	-	590.2	447	505	991.6	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL045M4-525AXSP04	-	1079.4	806.3	918.9	1863.1	669.8	1084.7	816.4	925.6	1845.4	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL045M4-625AXSP04	-	1169.2	877.7	999.5	1996	-	1173.9	888.6	1005.6	1975.8	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL045M4-525AXSP02	-	1514.9	-	-	2690.5	-	1540.5	-	-	2681.7	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL045M4-625AXSP02	-	1642.5	-	-	2888.9	-	1669.3	-	-	2872.2	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL037M4-525AXSP08	-	517.7	387.6	441.7	890.2	-	520.1	392.3	444.1	880.6	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL037M4-625AXSP08	-	559.9	421.1	478.8	950.4	-	561.5	426.3	481.2	941.3	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL037M4-525AXSP04	-	1030.7	771.3	879.2	1773.1	-	1035.6	780.7	884	1756.6	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL037M4-625AXSP04	-	1115.1	837.1	952.1	1896.2	-	1118.5	847.7	958.2	1875.8	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL037M4-525AXSP02	-	1446.9	-	-	2566.6	-	1470.8	-	-	2551.2	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL037M4-625AXSP02	-	-	-	-	2743.1	-	-	-	-	2728.5	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL030M4-525AXSP08	-	496.8	371.8	423.9	851.9	-	498	376.5	425.8	842.3	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL030M4-625AXSP08	-	535.7	403.4	458.1	907.6	-	537	408	460.1	897.5	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL030M4-525AXSP04	-	989.2	740	843.8	1697	-	993.1	749.5	847.7	1680.3	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL030M4-625AXSP04	-	1065.7	801.9	911	1808.6	-	1069.7	812.5	916.3	1788.5	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL030M4-525AXSP02	-	1388.7	-	-	2458.3	-	1410	-	-	2442.1	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL030M4-625AXSP02	-	-	-	-	2621.2	-	-	-	-	2603	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL045N4-525AXSP08	-	526.9	393.4	448.5	905.7	327.7	528.5	398.1	451.7	897	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL045N4-625AXSP08	-	571.2	429.1	488.2	971.8	-	572.7	434.4	490.4	960.9	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL045N4-525AXSP04	-	1048.9	782.7	894.1	1806.5	-	1052.3	793.6	899	1789.2	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL045N4-625AXSP04	-	1137.6	854.3	970.6	1936.5	-	1140.7	864.9	976.7	1914.7	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL045N4-525AXSP02	-	1471.6	-	-	2610.4	-	1495.9	-	-	2597.9	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL045N4-625AXSP02	-	1595.1	-	-	2804	-	1621	-	-	2784.4	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL037N4-525AXSP08	-	511.5	382.7	436	878.7	-	513.4	386.9	438.6	868.6	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL037N4-625AXSP08	-	554.1	417.1	473.4	940.1	-	555	421.1	475.8	930	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL037N4-525AXSP04	-	1018.4	761.5	867.7	1750.4	-	1022.3	770	873	1732.6	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL037N4-625AXSP04	-	1102.2	829.1	942.6	1873.4	-	1105.7	838.5	946.3	1853.4	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL037N4-525AXSP02	-	1430.4	-	-	2534.3	-	1452.4	-	-	2516.8	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL037N4-625AXSP02	-	-	-	-	2713.8	-	-	-	-	2696.4	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL030N4-525AXSP08	-	480.5	360.4	410.5	822.4	-	481.8	364.5	412.5	813.6	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL030N4-625AXSP08	-	518.7	-	444	877.5	-	519.8	-	445.8	866.6	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL030N4-525AXSP04	-	956.8	717.2	817.1	1640.6	-	960.9	725.5	821.2	1623.1	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL030N4-625AXSP04	-	1033.3	-	882.9	1748.7	-	1035.6	-	886.7	1729.2	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL030N4-525AXSP02	-	1344.8	-	-	2374.7	-	1365.7	-	-	2360.1	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL030N4-625AXSP02	-	-	-	-	2535.5	-	-	-	-	2517.6	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL045M5-525AXSP08	-	542.2	405.3	461.8	934.1	336.7	544.8	410.3	465.1	926.5	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL045M5-625AXSP08	-	587.9	441.6	502	1001.8	-	590.2	447	505	991.6	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL045M5-525AXSP04	-	1079.4	806.3	918.9	1863.1	669.8	1084.7	816.4	925.6	1845.4	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL045M5-625AXSP04	-	1169.2	877.7	999.5	1996	-	1173.9	888.6	1005.6	1975.8	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL045M5-525AXSP02	-	1514.9	-	-	2690.5	-	1540.5	-	-	2681.7	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL045M5-625AXSP02	-	1642.5	-	-	2888.9	-	1669.3	-	-	2872.2	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL037M5-525AXSP08	-	517.7	387.6	441.7	890.2	-	520.1	392.3	444.1	880.6	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL037M5-625AXSP08	-	559.9	421.1	478.8	950.4	-	561.5	426.3	481.2	941.3	855	19.5	4"	684	12.9	4"	1026	27.4	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-DD33S2XL037M5-525AXSP04	-	1030.7	771.3	879.2	1773.1	-	1035.6	780.7	884	1756.6	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL037M5-625AXSP04	-	1115.1	837.1	952.1	1896.2	-	1118.5	847.7	958.2	1875.8	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL037M5-525AXSP02	-	1446.9	-	-	2566.6	-	1470.8	-	-	2551.2	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL037M5-625AXSP02	-	-	-	-	2743.1	-	-	-	-	2728.5	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL030M5-525AXSP08	-	496.8	371.8	423.9	851.9	-	498	376.5	425.8	842.3	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL030M5-625AXSP08	-	535.7	403.4	458.1	907.6	-	537	408	460.1	897.5	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL030M5-525AXSP04	-	989.2	740	843.8	1697	-	993.1	749.5	847.7	1680.3	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL030M5-625AXSP04	-	1065.7	801.9	911	1808.6	-	1069.7	812.5	916.3	1788.5	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL030M5-525AXSP02	-	1388.7	-	-	2458.3	-	1410	-	-	2442.1	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL030M5-625AXSP02	-	-	-	-	2621.2	-	-	-	-	2603	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL045N5-525AXSP08	-	526.9	393.4	448.5	905.7	327.7	528.5	398.1	451.7	897	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL045N5-625AXSP08	-	571.2	429.1	488.2	971.8	-	572.7	434.4	490.4	960.9	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL045N5-525AXSP04	-	1048.9	782.7	894.1	1806.5	-	1052.3	793.6	899	1789.2	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL045N5-625AXSP04	-	1137.6	854.3	970.6	1936.5	-	1140.7	864.9	976.7	1914.7	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL045N5-525AXSP02	-	1471.6	-	-	2610.4	-	1495.9	-	-	2597.9	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL045N5-625AXSP02	-	1595.1	-	-	2804	-	1621	-	-	2784.4	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL037N5-525AXSP08	-	511.5	382.7	436	878.7	-	513.4	386.9	438.6	868.6	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL037N5-625AXSP08	-	554.1	417.1	473.4	940.1	-	555	421.1	475.8	930	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL037N5-525AXSP04	-	1018.4	761.5	867.7	1750.4	-	1022.3	770	873	1732.6	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL037N5-625AXSP04	-	1102.2	829.1	942.6	1873.4	-	1105.7	838.5	946.3	1853.4	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL037N5-525AXSP02	-	1430.4	-	-	2534.3	-	1452.4	-	-	2516.8	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL037N5-625AXSP02	-	-	-	-	2713.8	-	-	-	-	2696.4	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"
EAW-DD33S1XL030N5-525AXSP08	-	480.5	360.4	410.5	822.4	-	481.8	364.5	412.5	813.6	708	19	4"	567	12.6	4"	850	26.6	4"
EAW-DD33S1XL030N5-625AXSP08	-	518.7	-	444	877.5	-	519.8	-	445.8	866.6	855	19.5	4"	684	12.9	4"	1026	27.4	4"
EAW-DD33S2XL030N5-525AXSP04	-	956.8	717.2	817.1	1640.6	-	960.9	725.5	821.2	1623.1	1429	21.1	4"	1143	13.9	4"	1714	24.4	6"
EAW-DD33S2XL030N5-625AXSP04	-	1033.3	-	882.9	1748.7	-	1035.6	-	886.7	1729.2	1722	17.8	6"	1377	15.2	4"	2066	25	6"
EAW-DD33S3XL030N5-525AXSP02	-	1344.8	-	-	2374.7	-	1365.7	-	-	2360.1	2870	15.4	6"	2296	10.2	6"	3443	21.7	6"
EAW-DD33S3XL030N5-625AXSP02	-	-	-	-	2535.5	-	-	-	-	2517.6	3443	16.9	6"	2755	11.1	6"	4132	18.7	(2) 6"

Note: "-" indicates flow rate is outside of unit capability

Evapco EAW Line Thermal Performance in USGPM - 30% Ethylene Glycol as Process Fluid

Range °F	10	10	15	15	9	10	10	15	15	9	First	First	First	Second	Second	Second	Third	Third	Third
Approach °F	5	10	10	12	18	5	10	10	12	18	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow	Flow
Dry Bulb Temperature °F	77	77	77	77	77	95	95	95	95	95	GPM	PSI	Inlet	GPM	PSI	Inlet	GPM	PSI	Inlet
EAW-VD15S1ZB370K4-625AXSP16	-	-	-	-	185.9	-	-	-	-	183.1	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB370K4-525AXSP16	-	103.6	-	-	174.7	-	103.2	-	-	172.3	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB370K4-425AXSP16	-	95.1	-	81.1	162.6	-	94.9	-	81.1	160.4	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB550K4-625AXSP16	-	126.1	-	-	210.4	-	125.6	-	-	207.6	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB550K4-525AXSP16	-	116.4	-	99.3	197	-	116.1	-	99.2	194.7	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB550K4-425AXSP16	-	106.5	79.8	90.7	182.7	-	106.3	80	90.7	180.5	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB750K4-625AXSP16	-	136.7	-	117.1	229.1	-	136.4	-	117	226.5	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB750K4-525AXSP16	-	126.2	95	107.6	214.3	-	125.9	95.3	107.7	212	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB750K4-425AXSP16	-	115.3	86.2	98.1	198.2	-	115.3	86.6	98.3	196.1	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB370K5-625AXSP16	-	-	-	-	185.9	-	-	-	-	183.1	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB370K5-525AXSP16	-	103.6	-	-	174.7	-	103.2	-	-	172.3	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB370K5-425AXSP16	-	95.1	-	81.1	162.6	-	94.9	-	81.1	160.4	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB550K5-625AXSP16	-	126.1	-	-	210.4	-	125.6	-	-	207.6	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB550K5-525AXSP16	-	116.4	-	99.3	197	-	116.1	-	99.2	194.7	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB550K5-425AXSP16	-	106.5	79.8	90.7	182.7	-	106.3	80	90.7	180.5	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB750K5-625AXSP16	-	136.7	-	117.1	229.1	-	136.4	-	117	226.5	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB750K5-525AXSP16	-	126.2	95	107.6	214.3	-	125.9	95.3	107.7	212	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB750K5-425AXSP16	-	115.3	86.2	98.1	198.2	-	115.3	86.6	98.3	196.1	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB370C4-625AXSP16	-	116.7	-	-	194.5	-	116.1	-	-	191.5	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB370C4-525AXSP16	-	108	-	92.3	182.3	-	107.6	-	92	179.8	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB370C4-425AXSP16	-	98.9	74.2	84.2	169.1	-	98.5	74.4	84.2	167	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB550C4-625AXSP16	-	132.7	-	113.6	221.9	-	132.1	-	113.4	219	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB550C4-525AXSP16	-	122.1	91.8	104.2	206.9	-	121.6	92.1	104.1	204.5	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB550C4-425AXSP16	-	111.2	83.2	94.7	191	-	110.9	83.5	94.6	188.6	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB750C4-625AXSP16	-	142.1	-	121.7	238.5	-	141.8	-	121.6	235.7	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB750C4-525AXSP16	-	130.8	98.3	111.6	222.6	-	130.5	98.8	111.5	220.1	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB750C4-425AXSP16	-	119.2	89.1	101.5	205.3	73.7	119.1	89.5	101.5	203	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB370C5-625AXSP16	-	116.7	-	-	194.5	-	116.1	-	-	191.5	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB370C5-525AXSP16	-	108	-	92.3	182.3	-	107.6	-	92	179.8	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB370C5-425AXSP16	-	98.9	74.2	84.2	169.1	-	98.5	74.4	84.2	167	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB550C5-625AXSP16	-	132.7	-	113.6	221.9	-	132.1	-	113.4	219	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB550C5-525AXSP16	-	122.1	91.8	104.2	206.9	-	121.6	92.1	104.1	204.5	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB550C5-425AXSP16	-	111.2	83.2	94.7	191	-	110.9	83.5	94.6	188.6	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB750C5-625AXSP16	-	142.1	-	121.7	238.5	-	141.8	-	121.6	235.7	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB750C5-525AXSP16	-	130.8	98.3	111.6	222.6	-	130.5	98.8	111.5	220.1	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB750C5-425AXSP16	-	119.2	89.1	101.5	205.3	73.7	119.1	89.5	101.5	203	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB370K8-625AXSP16	-	-	-	-	185.9	-	-	-	-	183.1	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB370K8-525AXSP16	-	103.6	-	-	174.7	-	103.2	-	-	172.3	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB370K8-425AXSP16	-	95.1	-	81.1	162.6	-	94.9	-	81.1	160.4	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB550K8-625AXSP16	-	126.1	-	-	210.4	-	125.6	-	-	207.6	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB550K8-525AXSP16	-	116.4	-	99.3	197	-	116.1	-	99.2	194.7	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB550K8-425AXSP16	-	106.5	79.8	90.7	182.7	-	106.3	80	90.7	180.5	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S1ZB750K8-625AXSP16	-	136.7	-	117.1	229.1	-	136.4	-	117	226.5	242	19.9	3"	194	16.3	2"	291	28	3"
EAW-VD15S1ZB750K8-525AXSP16	-	126.2	95	107.6	214.3	-	125.9	95.3	107.7	212	194	22.7	2"	155	14.9	2"	232	31.8	2"
EAW-VD15S1ZB750K8-425AXSP16	-	115.3	86.2	98.1	198.2	-	115.3	86.6	98.3	196.1	157	21.3	2"	126	17.2	1-1/2"	189	30	2"
EAW-VD15S2ZB370K4-625AXSP12	152.1	232.7	179.7	200.8	379.3	151.9	230.2	178.3	198.8	372.7	327	26.5	3"	262	17.5	3"	392	37.2	3"
EAW-VD15S2ZB370K4-525AXSP08	-	209.4	-	-	352.8	-	208.5	-	-	347.9	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB370K4-425AXSP08	-	193.5	-	164.9	330	-	192.7	-	164.7	325.6	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB550K4-625AXSP08	-	251.2	-	-	419.8	-	250.2	-	-	414.3	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB550K4-525AXSP08	-	235.4	-	201	398.5	-	234.7	-	200.7	393.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB550K4-425AXSP08	-	216.5	162.2	184.5	371.1	-	216.3	162.9	184.4	366.5	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB750K4-625AXSP08	-	272.7	-	233.2	457.1	-	272.1	-	233.1	451.4	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB750K4-525AXSP08	-	255.4	192.1	218	433.5	-	254.6	193	218	428.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB750K4-425AXSP08	-	234.9	175.6	199.8	402.8	-	234.2	176.3	199.9	398.9	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB370K5-625AXSP12	152.1	232.7	179.7	200.8	379.3	151.9	230.2	178.3	198.8	372.7	327	26.5	3"	262	17.5	3"	392	37.2	3"
EAW-VD15S2ZB370K5-525AXSP08	-	209.4	-	-	352.8	-	208.5	-	-	347.9	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB370K5-425AXSP08	-	193.5	-	164.9	330	-	192.7	-	164.7	325.6	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB550K5-625AXSP08	-	251.2	-	-	419.8	-	250.2	-	-	414.3	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB550K5-525AXSP08	-	235.4	-	201	398.5	-	234.7	-	200.7	393.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB550K5-425AXSP08	-	216.5	162.2	184.5	371.1	-	216.3	162.9	184.4	366.5	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB750K5-625AXSP08	-	272.7	-	233.2	457.1	-	272.1	-	233.1	451.4	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB750K5-525AXSP08	-	255.4	192.1	218	433.5	-	254.6	193	218	428.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB750K5-425AXSP08	-	234.9	175.6	199.8	402.8	-	234.2	176.3	199.9	398.9	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB370C4-625AXSP08	-	232.6	-	-	387.6	-	231.7	-	-	382.2	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB370C4-525AXSP08	-	218.3	-	186.4	368.2	-	217.4	-	186.2	363.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB370C4-425AXSP08	-	201.2	-	171.3	343.2	-	200.3	151.3	171.1	339	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB550C4-625AXSP08	-	264.4	-	226.2	442.9	-	263.2	-	225.9	437	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB550C4-525AXSP08	-	246.9	185.7	210.6	418.7	-	246.2	186.6	210.3	413.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB550C4-425AXSP08	-	226.3	169.2	192.7	388.1	-	225.6	169.9	192.5	383.1	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB750C4-625AXSP08	-	283.2	-	242.4	475.8	-	282.5	-	242.1	469.7	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB750C4-525AXSP08	-	264.6	199.1	225.7	449.9	-	264.4	199.8	225.8	444.7	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB750C4-425AXSP08	-	242.8	181.6	206.7	417.2	-	242.6	182.3	206.9	413.1	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB370C5-625AXSP08	-	232.6	-	-	387.6	-	231.7	-	-	382.2	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB370C5-525AXSP08	-	218.3	-	186.4	368.2	-	217.4	-	186.2	363.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB370C5-425AXSP08	-	201.2	-	171.3	343.2	-	200.3	151.3	171.1	339	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB550C5-625AXSP08	-	264.4	-	226.2	442.9	-	263.2	-	225.9	437	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB550C5-525AXSP08	-	246.9	185.7	210.6	418.7	-	246.2	186.6	210.3	413.2	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB550C5-425AXSP08	-	226.3	169.2	192.7	388.1	-	225.6	169.9	192.5	383.1	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB750C5-625AXSP08	-	283.2	-	242.4	475.8	-	282.5	-	242.1	469.7	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB750C5-525AXSP08	-	264.6	199.1	225.7	449.9	-	264.4	199.8	225.8	444.7	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB750C5-425AXSP08	-	242.8	181.6	206.7	417.2	-	242.6	182.3	206.9	413.1	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB370K8-625AXSP12	152.1	232.7	179.7	200.8	379.3	151.9	230.2	178.3	198.8	372.7	327	26.5	3"	262	17.5	3"	392	37.2	3"
EAW-VD15S2ZB370K8-525AXSP08	-	209.4	-	-	352.8	-	208.5	-	-	347.9	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB370K8-425AXSP08	-	193.5	-	164.9	330	-	192.7	-	164.7	325.6	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB550K8-625AXSP08	-	251.2	-	-	419.8	-	250.2	-	-	414.3	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB550K8-525AXSP08	-	235.4	-	201	398.5	-	234.7	-	200.7	393.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB550K8-425AXSP08	-	216.5	162.2	184.5	371.1	-	216.3	162.9	184.4	366.5	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S2ZB750K8-625AXSP08	-	272.7	-	233.2	457.1	-	272.1	-	233.1	451.4	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD15S2ZB750K8-525AXSP08	-	255.4	192.1	218	433.5	-	254.6	193	218	428.4	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD15S2ZB750K8-425AXSP08	-	234.9	175.6	199.8	402.8	-	234.2	176.3	199.9	398.9	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD15S3ZB370K4-625AXSP08	226.0	346.6	267.5	298.9	565.8	226.1	342.9	265.7	295.9	556.6	484	27.7	3"	388	18.3	3"	581	34.6	4"
EAW-VD15S3ZB370K4-525AXSP06	-	320.5	-	274.7	536.3	-	318.6	-	273.7	528.2	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB370K4-425AXSP06	-	293.3	221.2	250.5	497	-	291.6	221.2	249.4	490.4	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB550K4-625AXSP06	-	382.6	-	328.5	635.6	-	380.4	-	327	625.8	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB550K4-525AXSP06	-	360.5	273.2	308.7	606	-	358.8	273.4	307.7	597.4	545	19.2	4"	436	15.2	3"	654	27	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3ZB550K4-425AXSP06	203.4	328.3	247.2	280.1	559	205.6	326.9	247.6	279.8	552	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB750K4-625AXSP06	-	415.4	316.1	356.2	691.3	-	413.3	316.5	355.3	682.7	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB750K4-525AXSP06	-	391.4	296.1	334.5	659.5	-	389.5	296.3	333.9	651.6	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB750K4-425AXSP06	219.5	355.7	267.3	303.3	607.7	221.9	354.7	267.7	302.9	600	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB370K5-625AXSP08	226.0	346.6	267.5	298.9	565.8	226.1	342.9	265.7	295.9	556.6	484	27.7	3"	388	18.3	3"	581	34.6	4"
EAW-VD15S3ZB370K5-525AXSP06	-	320.5	-	274.7	536.3	-	318.6	-	273.7	528.2	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB370K5-425AXSP06	-	293.3	221.2	250.5	497	-	291.6	221.2	249.4	490.4	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB550K5-625AXSP06	-	382.6	-	328.5	635.6	-	380.4	-	327	625.8	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB550K5-525AXSP06	-	360.5	273.2	308.7	606	-	358.8	273.4	307.7	597.4	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB550K5-425AXSP06	203.4	328.3	247.2	280.1	559	205.6	326.9	247.6	279.8	552	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB750K5-625AXSP06	-	415.4	316.1	356.2	691.3	-	413.3	316.5	355.3	682.7	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB750K5-525AXSP06	-	391.4	296.1	334.5	659.5	-	389.5	296.3	333.9	651.6	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB750K5-425AXSP06	219.5	355.7	267.3	303.3	607.7	221.9	354.7	267.7	302.9	600	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB370C4-625AXSP08	236.1	362.4	279.1	312.4	592	235.8	358.6	277.2	309.3	582.3	484	27.7	3"	388	18.3	3"	581	34.6	4"
EAW-VD15S3ZB370C4-525AXSP06	-	334.2	253.9	286.2	559.8	-	332.3	253.7	285.3	552	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB370C4-425AXSP06	-	305	229.6	260.3	517.7	-	303.2	229.6	259.5	510.5	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB550C4-625AXSP06	-	402.7	306.7	345.4	670.5	-	400.3	306.8	344.3	660.8	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB550C4-525AXSP06	-	378.3	286.6	323.6	636.8	-	376.5	286.4	322.5	628.4	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB550C4-425AXSP06	212.1	342.7	257.9	292.5	584.6	213.9	341.6	257.9	291.6	577	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB750C4-625AXSP06	-	431.5	328.4	370.2	719.7	-	429.7	328.7	369.2	710.3	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB750C4-525AXSP06	253.5	405.7	307	346.9	685.3	256.1	404.5	307.3	346.4	676.5	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB750C4-425AXSP06	226.8	367.8	276.4	313.8	629.4	229.3	366.8	276.9	313.5	621.4	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB370C5-625AXSP08	236.1	362.4	279.1	312.4	592	235.8	358.6	277.2	309.3	582.3	484	27.7	3"	388	18.3	3"	581	34.6	4"
EAW-VD15S3ZB370C5-525AXSP06	-	334.2	253.9	286.2	559.8	-	332.3	253.7	285.3	552	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB370C5-425AXSP06	-	305	229.6	260.3	517.7	-	303.2	229.6	259.5	510.5	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB550C5-625AXSP06	-	402.7	306.7	345.4	670.5	-	400.3	306.8	344.3	660.8	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB550C5-525AXSP06	-	378.3	286.6	323.6	636.8	-	376.5	286.4	322.5	628.4	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB550C5-425AXSP06	212.1	342.7	257.9	292.5	584.6	213.9	341.6	257.9	291.6	577	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB750C5-625AXSP06	-	431.5	328.4	370.2	719.7	-	429.7	328.7	369.2	710.3	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB750C5-525AXSP06	253.5	405.7	307	346.9	685.3	256.1	404.5	307.3	346.4	676.5	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB750C5-425AXSP06	226.8	367.8	276.4	313.8	629.4	229.3	366.8	276.9	313.5	621.4	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB370K8-625AXSP08	226.0	346.6	267.5	298.9	565.8	226.1	342.9	265.7	295.9	556.6	484	27.7	3"	388	18.3	3"	581	34.6	4"
EAW-VD15S3ZB370K8-525AXSP06	-	320.5	-	274.7	536.3	-	318.6	-	273.7	528.2	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB370K8-425AXSP06	-	293.3	221.2	250.5	497	-	291.6	221.2	249.4	490.4	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB550K8-625AXSP06	-	382.6	-	328.5	635.6	-	380.4	-	327	625.8	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB550K8-525AXSP06	-	360.5	273.2	308.7	606	-	358.8	273.4	307.7	597.4	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB550K8-425AXSP06	203.4	328.3	247.2	280.1	559	205.6	326.9	247.6	279.8	552	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S3ZB750K8-625AXSP06	-	415.4	316.1	356.2	691.3	-	413.3	316.5	355.3	682.7	654	20	4"	523	13.2	4"	785	28.2	4"
EAW-VD15S3ZB750K8-525AXSP06	-	391.4	296.1	334.5	659.5	-	389.5	296.3	333.9	651.6	545	19.2	4"	436	15.2	3"	654	27	4"
EAW-VD15S3ZB750K8-425AXSP06	219.5	355.7	267.3	303.3	607.7	221.9	354.7	267.7	302.9	600	436	21.1	3"	349	13.9	3"	523	26	4"
EAW-VD15S4ZB370K4-625AXSP06	302.6	463.8	357.6	400	756.1	-	458.8	355.2	396.1	743.7	654	25.2	4"	523	16.6	4"	785	35.4	4"
EAW-VD15S4ZB370K4-525AXSP04	-	418.3	-	-	705.6	-	417.1	-	-	695.9	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB370K4-425AXSP04	-	383.4	-	326.5	654.8	-	382.5	-	326.3	646.9	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB550K4-625AXSP04	-	501.2	-	-	838.7	-	499.7	-	-	827.7	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB550K4-525AXSP04	-	470.1	-	401.3	796.9	-	468.8	-	401.4	786.7	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB550K4-425AXSP04	-	429.6	321.5	365.3	736	-	428.6	322.9	365.8	728	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB750K4-625AXSP04	-	543.9	-	465.2	913.2	-	542.8	-	465.5	901.8	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB750K4-525AXSP04	-	510.1	383.7	435.3	867.1	-	509.3	385.4	435.3	856.8	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB750K4-425AXSP04	-	465.1	347.4	395.4	799.9	-	464.7	349.5	395.8	791	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB370K5-625AXSP06	302.6	463.8	357.6	400	756.1	-	458.8	355.2	396.1	743.7	654	25.2	4"	523	16.6	4"	785	35.4	4"
EAW-VD15S4ZB370K5-525AXSP04	-	418.3	-	-	705.6	-	417.1	-	-	695.9	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB370K5-425AXSP04	-	383.4	-	326.5	654.8	-	382.5	-	326.3	646.9	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB550K5-625AXSP04	-	501.2	-	-	838.7	-	499.7	-	-	827.7	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB550K5-525AXSP04	-	470.1	-	401.3	796.9	-	468.8	-	401.4	786.7	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB550K5-425AXSP04	-	429.6	321.5	365.3	736	-	428.6	322.9	365.8	728	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB750K5-625AXSP04	-	543.9	-	465.2	913.2	-	542.8	-	465.5	901.8	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB750K5-525AXSP04	-	510.1	383.7	435.3	867.1	-	509.3	385.4	435.3	856.8	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB750K5-425AXSP04	-	465.1	347.4	395.4	799.9	-	464.7	349.5	395.8	791	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB370C4-625AXSP06	315.6	484.4	373.1	417.5	792	315.3	479.2	370.6	413.4	778.2	654	25.2	4"	523	16.6	4"	785	35.4	4"
EAW-VD15S4ZB370C4-525AXSP04	-	436.1	-	-	736.5	-	434.9	-	-	726.3	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB370C4-425AXSP04	-	398.7	-	339.7	681.8	-	397.7	-	338.9	672.5	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB550C4-625AXSP04	-	528	-	-	884.7	-	525.8	-	-	872.9	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB550C4-525AXSP04	-	493.2	-	421.2	837.3	-	491.7	-	420.6	826.4	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB550C4-425AXSP04	-	448.2	335.4	381.4	769.5	-	447.1	336.8	381.1	760.8	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB750C4-625AXSP04	-	565.6	-	483.4	950.5	-	564.2	-	483.6	939.4	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB750C4-525AXSP04	-	529.3	397.6	451.3	899.7	-	528	399.6	451.6	889.4	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB750C4-425AXSP04	-	480.8	359.1	409	828.3	-	480.5	361.4	409.5	819.1	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB370C5-625AXSP06	315.6	484.4	373.1	417.5	792	315.3	479.2	370.6	413.4	778.2	654	25.2	4"	523	16.6	4"	785	35.4	4"
EAW-VD15S4ZB370C5-525AXSP04	-	436.1	-	-	736.5	-	434.9	-	-	726.3	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB370C5-425AXSP04	-	398.7	-	339.7	681.8	-	397.7	-	338.9	672.5	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB550C5-625AXSP04	-	528	-	-	884.7	-	525.8	-	-	872.9	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB550C5-525AXSP04	-	493.2	-	421.2	837.3	-	491.7	-	420.6	826.4	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB550C5-425AXSP04	-	448.2	335.4	381.4	769.5	-	447.1	336.8	381.1	760.8	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB750C5-625AXSP04	-	565.6	-	483.4	950.5	-	564.2	-	483.6	939.4	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB750C5-525AXSP04	-	529.3	397.6	451.3	899.7	-	528	399.6	451.6	889.4	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB750C5-425AXSP04	-	480.8	359.1	409	828.3	-	480.5	361.4	409.5	819.1	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB370K8-625AXSP06	302.6	463.8	357.6	400	756.1	-	458.8	355.2	396.1	743.7	654	25.2	4"	523	16.6	4"	785	35.4	4"
EAW-VD15S4ZB370K8-525AXSP04	-	418.3	-	-	705.6	-	417.1	-	-	695.9	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB370K8-425AXSP04	-	383.4	-	326.5	654.8	-	382.5	-	326.3	646.9	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB550K8-625AXSP04	-	501.2	-	-	838.7	-	499.7	-	-	827.7	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB550K8-525AXSP04	-	470.1	-	401.3	796.9	-	468.8	-	401.4	786.7	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB550K8-425AXSP04	-	429.6	321.5	365.3	736	-	428.6	322.9	365.8	728	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S4ZB750K8-625AXSP04	-	543.9	-	465.2	913.2	-	542.8	-	465.5	901.8	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD15S4ZB750K8-525AXSP04	-	510.1	383.7	435.3	867.1	-	509.3	385.4	435.3	856.8	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD15S4ZB750K8-425AXSP04	-	465.1	347.4	395.4	799.9	-	464.7	349.5	395.8	791	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD15S5ZB370K4-625AXSP04	-	568.8	-	489.4	935.7	-	564.1	-	485.9	920.5	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB370K4-525AXSP04	-	535.7	408.1	459.7	892.8	-	531.7	407.1	456.9	879.3	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB370K4-425AXSP04	307.8	491	371.7	420.1	829.5	309.7	488.1	371	418.3	817.3	654	21.1	4"	523	13.9	4"	785	29.7	4"
EAW-VD15S5ZB550K4-625AXSP04	-	641.7	490.4	551.1	1060.5	-	636.4	489.2	547.9	1044.2	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB550K4-525AXSP04	380.3	602.5	457.3	516	1007.5	382.7	598.1	457	513.5	993.2	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB550K4-425AXSP02	-	-	-	-	870.8	-	-	-	-	866	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB750K4-625AXSP04	-	695.9	531.4	597.7	1154.9	-	692.4	531.2	595.3	1139.2	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB750K4-525AXSP04	411.8	653.2	495.8	559.2	1096.4	414.4	650.1	495.3	557.2	1081.9	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB750K4-425AXSP02	-	-	-	-	944.9	-	-	-	-	939.5	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB370K5-625AXSP04	-	568.8	-	489.4	935.7	-	564.1	-	485.9	920.5	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB370K5-525AXSP04	-	535.7	408.1	459.7	892.8	-	531.7	407.1	456.9	879.3	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB370K5-425AXSP04	307.80	491	371.7	420.1	829.5	309.7	488.1	371	418.3	817.3	654	21.1	4"	523	13.9	4"	785	29.7	4"
EAW-VD15S5ZB550K5-625AXSP04	-	641.7	490.4	551.1	1060.5	-	636.4	489.2	547.9	1044.2	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB550K5-525AXSP04	380.30	602.5	457.3	516	1007.5	382.7	598.1	457	513.5	993.2	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB550K5-425AXSP02	-	-	-	-	870.8	-	-	-	-	866	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB750K5-625AXSP04	-	695.9	531.4	597.7	1154.9	-	692.4	531.2	595.3	1139.2	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S5ZB750K5-525AXSP04	411.80	653.2	495.8	559.2	1096.4	414.4	650.1	495.3	557.2	1081.9	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB750K5-425AXSP02	-	-	-	-	944.9	-	-	-	-	939.5	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB370C4-625AXSP04	-	593.9	455.4	510.7	978.9	-	589.1	453.7	507.7	964.1	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB370C4-525AXSP04	-	558.5	425	479	931.9	-	554.5	424.1	476.1	917.9	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB370C4-425AXSP04	319.40	510.6	386	436.6	862.8	321.4	507.5	385.2	434.6	850.9	654	21.1	4"	523	13.9	4"	785	29.7	4"
EAW-VD15S5ZB550C4-625AXSP04	-	675.4	516.2	579.6	1118.8	-	670.6	514.2	576.9	1101.3	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB550C4-525AXSP04	398.80	631.4	479.9	540.9	1058.7	400.7	627.5	478.7	538.3	1043.4	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB550C4-425AXSP02	-	-	-	-	909.7	-	-	-	-	904.3	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB750C4-625AXSP04	461.10	723.8	552.1	621.2	1202.3	463.9	718.9	551	618.6	1185.3	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB750C4-525AXSP04	426.00	677.1	514	580	1139.3	429.6	674.1	513.8	577.4	1124.6	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB750C4-425AXSP02	-	-	-	-	977.7	-	-	-	-	973.7	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB370C5-625AXSP04	-	593.9	455.4	510.7	978.9	-	589.1	453.7	507.7	964.1	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB370C5-525AXSP04	-	558.5	425	479	931.9	-	554.5	424.1	476.1	917.9	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB370C5-425AXSP04	319.40	510.6	386	436.6	862.8	321.4	507.5	385.2	434.6	850.9	654	21.1	4"	523	13.9	4"	785	29.7	4"
EAW-VD15S5ZB550C5-625AXSP04	-	675.4	516.2	579.6	1118.8	-	670.6	514.2	576.9	1101.3	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB550C5-525AXSP04	398.80	631.4	479.9	540.9	1058.7	400.7	627.5	478.7	538.3	1043.4	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB550C5-425AXSP02	-	-	-	-	909.7	-	-	-	-	904.3	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB750C5-625AXSP04	461.10	723.8	552.1	621.2	1202.3	463.9	718.9	551	618.6	1185.3	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB750C5-525AXSP04	426.00	677.1	514	580	1139.3	429.6	674.1	513.8	577.4	1124.6	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB750C5-425AXSP02	-	-	-	-	977.7	-	-	-	-	973.7	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB370K8-625AXSP04	-	568.8	-	489.4	935.7	-	564.1	-	485.9	920.5	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB370K8-525AXSP04	-	535.7	408.1	459.7	892.8	-	531.7	407.1	456.9	879.3	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB370K8-425AXSP04	307.80	491	371.7	420.1	829.5	309.7	488.1	371	418.3	817.3	654	21.1	4"	523	13.9	4"	785	29.7	4"
EAW-VD15S5ZB550K8-625AXSP04	-	641.7	490.4	551.1	1060.5	-	636.4	489.2	547.9	1044.2	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB550K8-525AXSP04	380.30	602.5	457.3	516	1007.5	382.7	598.1	457	513.5	993.2	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB550K8-425AXSP02	-	-	-	-	870.8	-	-	-	-	866	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S5ZB750K8-625AXSP04	-	695.9	531.4	597.7	1154.9	-	692.4	531.2	595.3	1139.2	981	20	(2) 4"	785	16.1	4"	1177	28	(2) 4"
EAW-VD15S5ZB750K8-525AXSP04	411.80	653.2	495.8	559.2	1096.4	414.4	650.1	495.3	557.2	1081.9	812	22.6	4"	649	14.9	4"	974	27.3	(2) 4"
EAW-VD15S5ZB750K8-425AXSP02	-	-	-	-	944.9	-	-	-	-	939.5	1308	11.9	(2) 4"	1046	7.8	(2) 4"	1570	16.7	(2) 4"
EAW-VD15S6ZB370K4-625AXSP04	-	692.4	533.6	597	1130.4	-	685	530	591.2	1111.9	981	23.4	(2) 4"	785	18.4	4"	1177	32.8	(2) 4"
EAW-VD15S6ZB370K4-525AXSP02	-	-	-	-	1027.5	-	-	-	-	1016.2	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB370K4-425AXSP02	-	-	-	-	947.6	-	-	-	-	938.1	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB550K4-625AXSP02	-	-	-	-	1220.1	-	-	-	-	1207.5	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB550K4-525AXSP02	-	-	-	-	1157.8	-	-	-	-	1147.9	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB550K4-425AXSP02	-	-	-	-	1063.6	-	608	-	-	1054.3	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB750K4-625AXSP02	-	-	-	-	1326.1	-	-	-	-	1314.9	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB750K4-525AXSP02	-	-	-	-	1258.7	-	-	-	-	1249.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB750K4-425AXSP02	-	654.3	-	-	1154.7	-	659.3	-	-	1146	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB370K5-625AXSP04	-	692.4	533.6	597	1130.4	-	685	530	591.2	1111.9	981	23.4	(2) 4"	785	18.4	4"	1177	32.8	(2) 4"
EAW-VD15S6ZB370K5-525AXSP02	-	-	-	-	1027.5	-	-	-	-	1016.2	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB370K5-425AXSP02	-	-	-	-	947.6	-	-	-	-	938.1	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB550K5-625AXSP02	-	-	-	-	1220.1	-	-	-	-	1207.5	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB550K5-525AXSP02	-	-	-	-	1157.8	-	-	-	-	1147.9	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB550K5-425AXSP02	-	-	-	-	1063.6	-	608	-	-	1054.3	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB750K5-625AXSP02	-	-	-	-	1326.1	-	-	-	-	1314.9	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB750K5-525AXSP02	-	-	-	-	1258.7	-	-	-	-	1249.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB750K5-425AXSP02	-	654.3	-	-	1154.7	-	659.3	-	-	1146	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB370C4-625AXSP04	470.90	723.1	557.5	623.9	1184	470.4	716.3	553.8	617.8	1163.4	981	23.4	(2) 4"	785	18.4	4"	1177	32.8	(2) 4"
EAW-VD15S6ZB370C4-525AXSP02	-	-	-	-	1072	-	-	-	-	1060.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB370C4-425AXSP02	-	-	-	-	984.9	-	-	-	-	976.2	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB550C4-625AXSP02	-	-	-	-	1286.5	-	-	-	-	1273	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB550C4-525AXSP02	-	-	-	-	1216	-	-	-	-	1205.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB550C4-425AXSP02	-	631.1	-	-	1111.4	-	634.7	-	-	1102.8	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB750C4-625AXSP02	-	-	-	-	1379.9	-	-	-	-	1367.6	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB750C4-525AXSP02	-	-	-	-	1307.4	-	-	-	-	1296.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB750C4-425AXSP02	-	676.9	-	-	1195.1	-	681	-	-	1186.1	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB370C5-625AXSP04	470.90	723.1	557.5	623.9	1184	470.4	716.3	553.8	617.8	1163.4	981	23.4	(2) 4"	785	18.4	4"	1177	32.8	(2) 4"
EAW-VD15S6ZB370C5-525AXSP02	-	-	-	-	1072	-	-	-	-	1060.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB370C5-425AXSP02	-	-	-	-	984.9	-	-	-	-	976.2	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB550C5-625AXSP02	-	-	-	-	1286.5	-	-	-	-	1273	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB550C5-525AXSP02	-	-	-	-	1216	-	-	-	-	1205.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB550C5-425AXSP02	-	631.1	-	-	1111.4	-	634.7	-	-	1102.8	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB750C5-625AXSP02	-	-	-	-	1379.9	-	-	-	-	1367.6	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB750C5-525AXSP02	-	-	-	-	1307.4	-	-	-	-	1296.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB750C5-425AXSP02	-	676.9	-	-	1195.1	-	681	-	-	1186.1	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB370K8-625AXSP04	-	692.4	533.6	597	1130.4	-	685	530	591.2	1111.9	981	23.4	(2) 4"	785	18.4	4"	1177	32.8	(2) 4"
EAW-VD15S6ZB370K8-525AXSP02	-	-	-	-	1027.5	-	-	-	-	1016.2	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB370K8-425AXSP02	-	-	-	-	947.6	-	-	-	-	938.1	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB550K8-625AXSP02	-	-	-	-	1220.1	-	-	-	-	1207.5	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB550K8-525AXSP02	-	-	-	-	1157.8	-	-	-	-	1147.9	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB550K8-425AXSP02	-	-	-	-	1063.6	-	608	-	-	1054.3	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S6ZB750K8-625AXSP02	-	-	-	-	1326.1	-	-	-	-	1314.9	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD15S6ZB750K8-525AXSP02	-	-	-	-	1258.7	-	-	-	-	1249.4	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD15S6ZB750K8-425AXSP02	-	654.3	-	-	1154.7	-	659.3	-	-	1146	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD15S1ZK370K4-625AXSP16	-	117.9	-	-	194.2	-	116.9	-	-	191.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK370K4-525AXSP16	-	109.3	-	93.6	182.9	-	108.5	-	93.3	180.2	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK370K4-425AXSP16	-	100.5	75.9	85.9	170.2	-	100	75.8	85.6	167.8	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK550K4-625AXSP16	-	133.3	-	114.4	220.7	-	132.4	-	113.9	217.4	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK550K4-525AXSP16	-	123.2	93.3	105.5	207.1	-	122.5	93.3	105	204	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK550K4-425AXSP16	-	112.8	85	96.3	191.9	-	112.4	85.1	96.1	189.4	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK750K4-625AXSP16	-	145.3	-	124.7	241.5	-	144.5	-	124.1	238.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK750K4-525AXSP16	-	134.1	101.4	114.6	226	-	133.3	101.4	114.3	222.8	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK750K4-425AXSP12	-	120.4	-	102.2	208.9	-	120.5	-	102.6	206.6	218	20.1	2"	174	13.2	2"	262	22.7	3"
EAW-VD15S1ZK370K5-625AXSP16	-	117.9	-	-	194.2	-	116.9	-	-	191.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK370K5-525AXSP16	-	109.3	-	93.6	182.9	-	108.5	-	93.3	180.2	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK370K5-425AXSP16	-	100.5	75.9	85.9	170.2	-	100	75.8	85.6	167.8	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK550K5-625AXSP16	-	133.3	-	114.4	220.7	-	132.4	-	113.9	217.4	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK550K5-525AXSP16	-	123.2	93.3	105.5	207.1	-	122.5	93.3	105	204	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK550K5-425AXSP16	-	112.8	85	96.3	191.9	-	112.4	85.1	96.1	189.4	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK750K5-625AXSP16	-	145.3	-	124.7	241.5	-	144.5	-	124.1	238.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK750K5-525AXSP16	-	134.1	101.4	114.6	226	-	133.3	101.4	114.3	222.8	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK750K5-425AXSP12	-	120.4	-	102.2	208.9	-	120.5	-	102.6	206.6	218	20.1	2"	174	13.2	2"	262	22.7	3"
EAW-VD15S1ZK370C4-625AXSP16	-	123.2	-	-	203.4	-	122.2	-	-	200.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK370C4-525AXSP16	-	113.9	-	97.6	190.8	-	113.2	-	97.1	187.9	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK370C4-425AXSP16	-	104.3	78.8	89.1	176.9	-	103.8	78.7	88.7	174.4	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK550C4-625AXSP16	-	140.3	-	120.3	232.8	-	139.3	-	119.8	229.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK550C4-525AXSP16	-	129	97.7	110.5	217.1	-	128.2	97.6	110	214	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK550C4-425AXSP16	-	117.6	88.5	100.4	200.4	73.4	116.9	88.5	100	197.6	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK750C4-625AXSP16	-	151	115	129.5	251.2	-	150.2	114.9	129	248	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK750C4-525AXSP16	-	138.9	104.9	118.8	234.5	-	138.4	105.1	118.3	231.4	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK750C4-425AXSP12	-	124.5	-	105.6	216.1	-	124.7	-	106	214	218	20.1	2"	174	13.2	2"	262	22.7	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1ZK370C5-625AXSP16	-	123.2	-	-	203.4	-	122.2	-	-	200.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK370C5-525AXSP16	-	113.9	-	97.6	190.8	-	113.2	-	97.1	187.9	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK370C5-425AXSP16	-	104.3	78.8	89.1	176.9	-	103.8	78.7	88.7	174.4	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK550C5-625AXSP16	-	140.3	-	120.3	232.8	-	139.3	-	119.8	229.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK550C5-525AXSP16	-	129	97.7	110.5	217.1	-	128.2	97.6	110	214	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK550C5-425AXSP16	-	117.6	88.5	100.4	200.4	73.4	116.9	88.5	100	197.6	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK750C5-625AXSP16	-	151	115	129.5	251.2	-	150.2	114.9	129	248	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK750C5-525AXSP16	-	138.9	104.9	118.8	234.5	-	138.4	105.1	118.3	231.4	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK750C5-425AXSP12	-	124.5	-	105.6	216.1	-	124.7	-	106	214	218	20.1	2"	174	13.2	2"	262	22.7	3"
EAW-VD15S1ZK370K8-625AXSP16	-	117.9	-	-	194.2	-	116.9	-	-	191.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK370K8-525AXSP16	-	109.3	-	93.6	182.9	-	108.5	-	93.3	180.2	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK370K8-425AXSP16	-	100.5	75.9	85.9	170.2	-	100	75.8	85.6	167.8	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK550K8-625AXSP16	-	133.3	-	114.4	220.7	-	132.4	-	113.9	217.4	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK550K8-525AXSP16	-	123.2	93.3	105.5	207.1	-	122.5	93.3	105	204	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK550K8-425AXSP16	-	112.8	85	96.3	191.9	-	112.4	85.1	96.1	189.4	157	22.9	2"	126	18.2	1-1/2"	189	32.1	2"
EAW-VD15S1ZK750K8-625AXSP16	-	145.3	-	124.7	241.5	-	144.5	-	124.1	238.1	242	21.5	3"	194	17.3	2"	291	30.1	3"
EAW-VD15S1ZK750K8-525AXSP16	-	134.1	101.4	114.6	226	-	133.3	101.4	114.3	222.8	194	24.2	2"	155	16	2"	232	34	2"
EAW-VD15S1ZK750K8-425AXSP12	-	120.4	-	102.2	208.9	-	120.5	-	102.6	206.6	218	20.1	2"	174	13.2	2"	262	22.7	3"
EAW-VD15S2ZK370K4-625AXSP08	-	234.9	-	-	387.6	-	233	-	-	381.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK370K4-525AXSP08	-	220.9	-	189.4	369.3	-	219.4	-	188.3	363.4	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK370K4-425AXSP08	-	204.3	154.2	174.5	345.4	-	203.2	154	173.8	340.4	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK550K4-625AXSP08	-	265.7	-	228.3	440.4	-	263.9	-	227	433.7	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK550K4-525AXSP08	-	249.1	188.9	213.1	418.3	-	247.7	188.9	212.5	412	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK550K4-425AXSP08	-	229.4	172.9	196	389.6	-	228.5	173	195.2	384.4	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK750K4-625AXSP08	-	289.9	-	248.4	482	-	287.9	-	247.6	475.1	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK750K4-525AXSP08	-	271.2	205.1	232	456.6	-	269.6	205.3	231.3	450.2	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK750K4-425AXSP08	154.10	249.4	187.6	212.6	424.9	155.7	248.3	187.7	212.1	419	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK370K5-625AXSP08	-	234.9	-	-	387.6	-	233	-	-	381.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK370K5-525AXSP08	-	220.9	-	189.4	369.3	-	219.4	-	188.3	363.4	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK370K5-425AXSP08	-	204.3	154.2	174.5	345.4	-	203.2	154	173.8	340.4	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK550K5-625AXSP08	-	265.7	-	228.3	440.4	-	263.9	-	227	433.7	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK550K5-525AXSP08	-	249.1	188.9	213.1	418.3	-	247.7	188.9	212.5	412	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK550K5-425AXSP08	-	229.4	172.9	196	389.6	-	228.5	173	195.2	384.4	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK750K5-625AXSP08	-	289.9	-	248.4	482	-	287.9	-	247.6	475.1	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK750K5-525AXSP08	-	271.2	205.1	232	456.6	-	269.6	205.3	231.3	450.2	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK750K5-425AXSP08	154.10	249.4	187.6	212.6	424.9	155.7	248.3	187.7	212.1	419	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK370C4-625AXSP08	-	245.5	-	-	405.8	-	243.6	-	-	398.8	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK370C4-525AXSP08	-	230.2	-	197.2	385.3	-	228.9	-	196.3	379.4	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK370C4-425AXSP08	-	212.1	159.9	181.3	359.1	-	210.9	159.9	180.3	353.8	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK550C4-625AXSP08	-	279.6	-	240	464.4	-	277.6	-	238.6	457.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK550C4-525AXSP08	-	260.8	197.8	223.2	438.6	-	259.2	197.6	222.5	432.2	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK550C4-425AXSP08	-	239.2	180	204.2	406.9	-	237.8	180	203.3	401.3	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK750C4-625AXSP08	-	300.8	228.9	257.9	501.3	-	299.3	229.2	257.3	494.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK750C4-525AXSP08	-	281.1	212.6	240.5	473.7	-	279.8	212.8	239.5	467.6	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK750C4-425AXSP08	159.00	257.6	193.9	219.8	439.6	160.7	256.5	193.9	219.2	434	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK370C5-625AXSP08	-	245.5	-	-	405.8	-	243.6	-	-	398.8	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK370C5-525AXSP08	-	230.2	-	197.2	385.3	-	228.9	-	196.3	379.4	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK370C5-425AXSP08	-	212.1	159.9	181.3	359.1	-	210.9	159.9	180.3	353.8	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK550C5-625AXSP08	-	279.6	-	240	464.4	-	277.6	-	238.6	457.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK550C5-525AXSP08	-	260.8	197.8	223.2	438.6	-	259.2	197.6	222.5	432.2	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK550C5-425AXSP08	-	239.2	180	204.2	406.9	-	237.8	180	203.3	401.3	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK750C5-625AXSP08	-	300.8	228.9	257.9	501.3	-	299.3	229.2	257.3	494.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK750C5-525AXSP08	-	281.1	212.6	240.5	473.7	-	279.8	212.8	239.5	467.6	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK750C5-425AXSP08	159.00	257.6	193.9	219.8	439.6	160.7	256.5	193.9	219.2	434	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK370K8-625AXSP08	-	234.9	-	-	387.6	-	233	-	-	381.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK370K8-525AXSP08	-	220.9	-	189.4	369.3	-	219.4	-	188.3	363.4	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK370K8-425AXSP08	-	204.3	154.2	174.5	345.4	-	203.2	154	173.8	340.4	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK550K8-625AXSP08	-	265.7	-	228.3	440.4	-	263.9	-	227	433.7	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK550K8-525AXSP08	-	249.1	188.9	213.1	418.3	-	247.7	188.9	212.5	412	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK550K8-425AXSP08	-	229.4	172.9	196	389.6	-	228.5	173	195.2	384.4	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S2ZK750K8-625AXSP08	-	289.9	-	248.4	482	-	287.9	-	247.6	475.1	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD15S2ZK750K8-525AXSP08	-	271.2	205.1	232	456.6	-	269.6	205.3	231.3	450.2	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD15S2ZK750K8-425AXSP08	154.10	249.4	187.6	212.6	424.9	155.7	248.3	187.7	212.1	419	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD15S3ZK370K4-625AXSP06	-	357.4	-	307.5	585.8	-	353.7	-	304.9	575.8	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK370K4-525AXSP06	-	337.9	257.7	290	560.5	-	335	256.8	287.9	551.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK370K4-425AXSP06	-	309.1	234.3	264.6	520.1	-	306.9	233.6	263.1	511.9	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK550K4-625AXSP06	-	404.5	309.7	347.8	665.9	-	400.7	308.6	345.3	655.7	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK550K4-525AXSP06	-	381.3	290.3	327.1	635.2	-	378	289.6	325.1	625.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK550K4-425AXSP06	217.60	347.3	262.9	296.9	586.7	218.6	345.3	262.1	295.6	578.8	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK750K4-625AXSP06	-	440.9	337.3	378.6	728.8	-	437.2	336	376.4	717.5	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK750K4-525AXSP06	262.20	414.8	315.3	355.7	694.4	263.8	412.2	315	354	684.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK750K4-425AXSP04	-	356.5	-	302.4	620.4	-	357.7	-	304.1	613.8	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S3ZK370K5-625AXSP06	-	357.4	-	307.5	585.8	-	353.7	-	304.9	575.8	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK370K5-525AXSP06	-	337.9	257.7	290	560.5	-	335	256.8	287.9	551.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK370K5-425AXSP06	-	309.1	234.3	264.6	520.1	-	306.9	233.6	263.1	511.9	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK550K5-625AXSP06	-	404.5	309.7	347.8	665.9	-	400.7	308.6	345.3	655.7	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK550K5-525AXSP06	-	381.3	290.3	327.1	635.2	-	378	289.6	325.1	625.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK550K5-425AXSP06	217.60	347.3	262.9	296.9	586.7	218.6	345.3	262.1	295.6	578.8	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK750K5-625AXSP06	-	440.9	337.3	378.6	728.8	-	437.2	336	376.4	717.5	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK750K5-525AXSP06	262.20	414.8	315.3	355.7	694.4	263.8	412.2	315	354	684.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK750K5-425AXSP04	-	356.5	-	302.4	620.4	-	357.7	-	304.1	613.8	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S3ZK370C4-625AXSP06	-	373.1	-	321.2	612.8	-	369.7	-	318.6	602.9	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK370C4-525AXSP06	-	352.2	268.8	302.1	585.6	-	349.1	267.7	300.2	575.9	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK370C4-425AXSP06	-	321	243.4	274.5	540.8	202.6	318.6	242.6	272.9	532.8	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK550C4-625AXSP06	-	425.1	325.6	365.8	702.3	-	421.6	324.3	363.1	690.5	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK550C4-525AXSP06	252.90	399.3	303.9	342.2	666.9	254	396.2	302.7	339.9	656.3	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK550C4-425AXSP04	-	342.3	-	-	594.4	-	342.7	-	-	588	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S3ZK750C4-625AXSP06	-	458.2	350.2	393.3	758.1	-	454.6	349	391.1	747.4	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK750C4-525AXSP06	271.70	430.5	326.9	368.4	720.6	273.4	427.3	326.1	366.6	710.2	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK750C4-425AXSP04	-	368.7	-	312.4	641.7	-	369.8	-	314.1	635.6	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S3ZK370C5-625AXSP06	-	373.1	-	321.2	612.8	-	369.7	-	318.6	602.9	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK370C5-525AXSP06	-	352.2	268.8	302.1	585.6	-	349.1	267.7	300.2	575.9	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK370C5-425AXSP06	-	321	243.4	274.5	540.8	202.6	318.6	242.6	272.9	532.8	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK550C5-625AXSP06	-	425.1	325.6	365.8	702.3	-	421.6	324.3	363.1	690.5	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK550C5-525AXSP06	252.90	399.3	303.9	342.2	666.9	254	396.2	302.7	339.9	656.3	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK550C5-425AXSP04	-	342.3	-	-	594.4	-	342.7	-	-	588	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S3ZK750C5-625AXSP06	-	458.2	350.2	393.3	758.1	-	454.6	349	391.1	747.4	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK750C5-525AXSP06	271.70	430.5	326.9	368.4	720.6	273.4	427.3	326.1	366.6	710.2	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK750C5-425AXSP04	-	368.7	-	312.4	641.7	-	369.8	-	314.1	635.6	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S3ZK370K8-625AXSP06	-	357.4	-	307.5	585.8	-	353.7	-	304.9	575.8	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK370K8-525AXSP06	-	337.9	257.7	290	560.5	-	335	256.8	287.9	551.5	545	20.9	4"	436	16.3	3"	654	29.4	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3ZK370K8-425AXSP06	-	309.1	234.3	264.6	520.1	-	306.9	233.6	263.1	511.9	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK550K8-625AXSP06	-	404.5	309.7	347.8	665.9	-	400.7	308.6	345.3	655.7	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK550K8-525AXSP06	-	381.3	290.3	327.1	635.2	-	378	289.6	325.1	625.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK550K8-425AXSP06	217.60	347.3	262.9	296.9	586.7	218.6	345.3	262.1	295.6	578.8	436	22.8	3"	349	15	3"	523	28.4	4"
EAW-VD15S3ZK750K8-625AXSP06	-	440.9	337.3	378.6	728.8	-	437.2	336	376.4	717.5	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD15S3ZK750K8-525AXSP06	262.20	414.8	315.3	355.7	694.4	263.8	412.2	315	354	684.5	545	20.9	4"	436	16.3	3"	654	29.4	4"
EAW-VD15S3ZK750K8-425AXSP04	-	356.5	-	302.4	620.4	-	357.7	-	304.1	613.8	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD15S4ZK370K4-625AXSP04	-	469.2	-	-	774.2	-	465.5	-	-	761.8	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK370K4-525AXSP04	-	441.8	-	378.2	738.6	-	438.7	-	376.6	726.7	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK370K4-425AXSP04	-	405	305.4	345.7	686.3	-	402.8	305.6	344.4	676.4	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK550K4-625AXSP04	-	530.7	-	455.3	879.9	-	527.2	-	-	866.5	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK550K4-525AXSP04	-	498.2	377.3	426.2	836.7	-	495.4	377.2	424.4	824	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK550K4-425AXSP04	-	454.7	342.4	388.3	773.9	-	452.9	342.6	387.4	763.6	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK750K4-625AXSP04	-	578.3	-	496.1	962.8	-	575.1	-	494	949.1	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK750K4-525AXSP04	-	541.7	409.6	463.2	913.2	-	539.3	410.1	461.9	901.4	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK750K4-425AXSP04	304.70	494.1	371.3	421	842.6	308.1	492.1	372.1	420.7	832.3	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK370K5-625AXSP04	-	469.2	-	-	774.2	-	465.5	-	-	761.8	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK370K5-525AXSP04	-	441.8	-	378.2	738.6	-	438.7	-	376.6	726.7	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK370K5-425AXSP04	-	405	305.4	345.7	686.3	-	402.8	305.6	344.4	676.4	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK550K5-625AXSP04	-	530.7	-	455.3	879.9	-	527.2	-	-	866.5	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK550K5-525AXSP04	-	498.2	377.3	426.2	836.7	-	495.4	377.2	424.4	824	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK550K5-425AXSP04	-	454.7	342.4	388.3	773.9	-	452.9	342.6	387.4	763.6	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK750K5-625AXSP04	-	578.3	-	496.1	962.8	-	575.1	-	494	949.1	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK750K5-525AXSP04	-	541.7	409.6	463.2	913.2	-	539.3	410.1	461.9	901.4	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK750K5-425AXSP04	304.70	494.1	371.3	421	842.6	308.1	492.1	372.1	420.7	832.3	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK370C4-625AXSP04	-	490.3	-	-	810.7	-	486.5	-	-	797.7	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK370C4-525AXSP04	-	460.4	-	394.5	770.6	-	457.1	-	392.1	758.9	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK370C4-425AXSP04	-	420.5	317.2	359.2	713.5	-	418.2	316.8	357.8	703.1	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK550C4-625AXSP04	-	558.4	-	478.7	927.8	-	554.6	-	476.7	913.5	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK550C4-525AXSP04	-	521.6	395	446.4	877.2	-	518.4	394.7	444.3	864.5	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK550C4-425AXSP04	-	474.1	356.9	404.4	808.2	-	472.1	357.1	403.4	797.1	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK750C4-625AXSP04	-	600.9	457.2	515.2	1001.4	-	597.8	457.2	513.2	987.4	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK750C4-525AXSP04	-	562.1	424.5	480.3	947.5	-	559.6	425	478.9	935.2	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK750C4-425AXSP04	314.50	511.2	383.6	435.2	873.1	318	509	384.4	434.8	862	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK370C5-625AXSP04	-	490.3	-	-	810.7	-	486.5	-	-	797.7	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK370C5-525AXSP04	-	460.4	-	394.5	770.6	-	457.1	-	392.1	758.9	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK370C5-425AXSP04	-	420.5	317.2	359.2	713.5	-	418.2	316.8	357.8	703.1	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK550C5-625AXSP04	-	558.4	-	478.7	927.8	-	554.6	-	476.7	913.5	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK550C5-525AXSP04	-	521.6	395	446.4	877.2	-	518.4	394.7	444.3	864.5	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK550C5-425AXSP04	-	474.1	356.9	404.4	808.2	-	472.1	357.1	403.4	797.1	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK750C5-625AXSP04	-	600.9	457.2	515.2	1001.4	-	597.8	457.2	513.2	987.4	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK750C5-525AXSP04	-	562.1	424.5	480.3	947.5	-	559.6	425	478.9	935.2	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK750C5-425AXSP04	314.50	511.2	383.6	435.2	873.1	318	509	384.4	434.8	862	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK370K8-625AXSP04	-	469.2	-	-	774.2	-	465.5	-	-	761.8	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK370K8-525AXSP04	-	441.8	-	378.2	738.6	-	438.7	-	376.6	726.7	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK370K8-425AXSP04	-	405	305.4	345.7	686.3	-	402.8	305.6	344.4	676.4	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK550K8-625AXSP04	-	530.7	-	455.3	879.9	-	527.2	-	-	866.5	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK550K8-525AXSP04	-	498.2	377.3	426.2	836.7	-	495.4	377.2	424.4	824	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK550K8-425AXSP04	-	454.7	342.4	388.3	773.9	-	452.9	342.6	387.4	763.6	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S4ZK750K8-625AXSP04	-	578.3	-	496.1	962.8	-	575.1	-	494	949.1	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD15S4ZK750K8-525AXSP04	-	541.7	409.6	463.2	913.2	-	539.3	410.1	461.9	901.4	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD15S4ZK750K8-425AXSP04	304.70	494.1	371.3	421	842.6	308.1	492.1	372.1	420.7	832.3	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD15S5ZK370K4-625AXSP04	-	598.5	460.5	515.7	977.5	-	591.5	457.5	510.8	960.6	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK370K4-525AXSP04	-	563.8	431.4	484.7	933.1	-	558.3	429.1	480.4	917	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK370K4-425AXSP02	-	-	-	-	816.1	-	-	-	-	809.3	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550K4-625AXSP04	-	676.6	520.4	582.7	1111.1	-	670.2	517	577.8	1092.9	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK550K4-525AXSP04	406.00	635.5	485.2	545.9	1056.1	407.1	630	483.3	541.8	1040.1	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK550K4-425AXSP02	-	-	-	-	919.7	-	-	-	-	912	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750K4-625AXSP04	475.60	737.6	566.1	635.2	1216.1	476.6	731.4	563.8	630.5	1197.2	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK750K4-525AXSP02	-	-	-	-	1092.7	-	-	-	-	1083.4	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK750K4-425AXSP02	-	-	-	-	999.9	-	-	-	-	992.8	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370K5-625AXSP04	-	598.5	460.5	515.7	977.5	-	591.5	457.5	510.8	960.6	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK370K5-525AXSP04	-	563.8	431.4	484.7	933.1	-	558.3	429.1	480.4	917	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK370K5-425AXSP02	-	-	-	-	816.1	-	-	-	-	809.3	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550K5-625AXSP04	-	676.6	520.4	582.7	1111.1	-	670.2	517	577.8	1092.9	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK550K5-525AXSP04	406.00	635.5	485.2	545.9	1056.1	407.1	630	483.3	541.8	1040.1	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK550K5-425AXSP02	-	-	-	-	919.7	-	-	-	-	912	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750K5-625AXSP04	475.60	737.6	566.1	635.2	1216.1	476.6	731.4	563.8	630.5	1197.2	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK750K5-525AXSP02	-	-	-	-	1092.7	-	-	-	-	1083.4	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK750K5-425AXSP02	-	-	-	-	999.9	-	-	-	-	992.8	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370C4-625AXSP04	-	624.9	480.9	538.8	1022.4	-	618.4	477.9	533.7	1004.8	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK370C4-525AXSP04	376.20	587.8	449.2	504.9	973.7	377.1	581.8	446.7	500.3	957.6	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK370C4-425AXSP02	-	-	-	-	849.1	-	-	-	-	840.7	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550C4-625AXSP04	459.80	712.1	546.3	612.8	1171.8	460.1	705.2	543.4	607.5	1152.2	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK550C4-525AXSP02	-	-	-	-	1050	-	-	-	-	1039.4	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK550C4-425AXSP02	-	-	-	-	959.9	-	-	-	-	951.4	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750C4-625AXSP04	493.70	766.6	587.8	659.8	1264.9	494.9	760.4	584.9	655.2	1245.7	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK750C4-525AXSP02	-	-	-	-	1133.1	-	-	-	-	1123.5	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK750C4-425AXSP02	-	-	-	-	1035.4	-	-	-	-	1027.7	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370C5-625AXSP04	-	624.9	480.9	538.8	1022.4	-	618.4	477.9	533.7	1004.8	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK370C5-525AXSP04	376.20	587.8	449.2	504.9	973.7	377.1	581.8	446.7	500.3	957.6	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK370C5-425AXSP02	-	-	-	-	849.1	-	-	-	-	840.7	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550C5-625AXSP04	459.80	712.1	546.3	612.8	1171.8	460.1	705.2	543.4	607.5	1152.2	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK550C5-525AXSP02	-	-	-	-	1050	-	-	-	-	1039.4	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK550C5-425AXSP02	-	-	-	-	959.9	-	-	-	-	951.4	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750C5-625AXSP04	493.70	766.6	587.8	659.8	1264.9	494.9	760.4	584.9	655.2	1245.7	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK750C5-525AXSP02	-	-	-	-	1133.1	-	-	-	-	1123.5	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK750C5-425AXSP02	-	-	-	-	1035.4	-	-	-	-	1027.7	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK370K8-625AXSP04	-	598.5	460.5	515.7	977.5	-	591.5	457.5	510.8	960.6	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK370K8-525AXSP04	-	563.8	431.4	484.7	933.1	-	558.3	429.1	480.4	917	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK370K8-425AXSP02	-	-	-	-	816.1	-	-	-	-	809.3	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK550K8-625AXSP04	-	676.6	520.4	582.7	1111.1	-	670.2	517	577.8	1092.9	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK550K8-525AXSP04	406.00	635.5	485.2	545.9	1056.1	407.1	630	483.3	541.8	1040.1	812	24.5	4"	649	16.1	4"	974	30	(2) 4"
EAW-VD15S5ZK550K8-425AXSP02	-	-	-	-	919.7	-	-	-	-	912	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S5ZK750K8-625AXSP04	475.60	737.6	566.1	635.2	1216.1	476.6	731.4	563.8	630.5	1197.2	981	21.9	(2) 4"	785	17.4	4"	1177	30.7	(2) 4"
EAW-VD15S5ZK750K8-525AXSP02	-	-	-	-	1092.7	-	-	-	-	1083.4	1635	14.3	(2) 4"	1308	9.4	(2) 4"	1962	16.9	(3) 4"
EAW-VD15S5ZK750K8-425AXSP02	-	-	-	-	999.9	-	-	-	-	992.8	1308	12.8	(2) 4"	1046	8.4	(2) 4"	1570	18.1	(2) 4"
EAW-VD15S6ZK370K4-625AXSP04	478.20	726.7	562.6	628.1	1180.7	476.3	718.1	557.4	620.4	1159.1	981	25.7	(2) 4"	785	19.9	4"	1177	36.1	(2) 4"
EAW-VD15S6ZK370K4-525AXSP02	-	-	-	-	1077.4	-	-	-	-	1064.4	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK370K4-425AXSP02	-	-	-	-	995.5	-	-	-	-	984.4	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK550K4-625AXSP02	-	-	-	-	1283.7	-	-	-	-	1267.6	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6ZK550K4-525AXSP02	-	-	-	-	1219.5	-	-	-	-	1206.1	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK550K4-425AXSP02	-	644.4	-	-	1121.1	-	645.8	-	-	1109.9	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK750K4-625AXSP02	-	-	-	-	1402.3	-	-	-	-	1387.7	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK750K4-525AXSP02	-	772.8	-	-	1330.2	-	774.7	-	-	1316.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK750K4-425AXSP02	-	700.1	-	-	1219.5	-	701.6	-	-	1208.6	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK370K5-625AXSP04	478.20	726.7	562.6	628.1	1180.7	476.3	718.1	557.4	620.4	1159.1	981	25.7	(2) 4"	785	19.9	4"	1177	36.1	(2) 4"
EAW-VD15S6ZK370K5-525AXSP02	-	-	-	-	1077.4	-	-	-	-	1064.4	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK370K5-425AXSP02	-	-	-	-	995.5	-	-	-	-	984.4	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK550K5-625AXSP02	-	-	-	-	1283.7	-	-	-	-	1267.6	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK550K5-525AXSP02	-	-	-	-	1219.5	-	-	-	-	1206.1	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK550K5-425AXSP02	-	644.4	-	-	1121.1	-	645.8	-	-	1109.9	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK750K5-625AXSP02	-	-	-	-	1402.3	-	-	-	-	1387.7	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK750K5-525AXSP02	-	772.8	-	-	1330.2	-	774.7	-	-	1316.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK750K5-425AXSP02	-	700.1	-	-	1219.5	-	701.6	-	-	1208.6	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK370C4-625AXSP02	-	-	-	-	1183.4	-	-	-	-	1167.4	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK370C4-525AXSP02	-	-	-	-	1125.2	-	-	-	-	1111.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK370C4-425AXSP02	-	-	-	-	1034.6	-	-	-	-	1022.7	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK550C4-625AXSP02	-	-	-	-	1351.7	-	-	-	-	1335.9	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK550C4-525AXSP02	-	-	-	-	1279.7	-	-	-	-	1264.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK550C4-425AXSP02	-	671.2	-	-	1170.3	-	672.6	-	-	1158.1	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK750C4-625AXSP02	-	-	-	-	1459.9	-	-	-	-	1443.4	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK750C4-525AXSP02	-	801.4	-	-	1381.4	-	802.3	-	-	1367.5	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK750C4-425AXSP02	-	723.8	-	612.6	1263	-	725.3	-	616.3	1251.4	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK370C5-625AXSP02	-	-	-	-	1183.4	-	-	-	-	1167.4	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK370C5-525AXSP02	-	-	-	-	1125.2	-	-	-	-	1111.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK370C5-425AXSP02	-	-	-	-	1034.6	-	-	-	-	1022.7	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK550C5-625AXSP02	-	-	-	-	1351.7	-	-	-	-	1335.9	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK550C5-525AXSP02	-	-	-	-	1279.7	-	-	-	-	1264.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK550C5-425AXSP02	-	671.2	-	-	1170.3	-	672.6	-	-	1158.1	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK750C5-625AXSP02	-	-	-	-	1459.9	-	-	-	-	1443.4	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK750C5-525AXSP02	-	801.4	-	-	1381.4	-	802.3	-	-	1367.5	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK750C5-425AXSP02	-	723.8	-	612.6	1263	-	725.3	-	616.3	1251.4	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK370K8-625AXSP04	478.20	726.7	562.6	628.1	1180.7	476.3	718.1	557.4	620.4	1159.1	981	25.7	(2) 4"	785	19.9	4"	1177	36.1	(2) 4"
EAW-VD15S6ZK370K8-525AXSP02	-	-	-	-	1077.4	-	-	-	-	1064.4	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK370K8-425AXSP02	-	-	-	-	995.5	-	-	-	-	984.4	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK550K8-625AXSP02	-	-	-	-	1283.7	-	-	-	-	1267.6	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK550K8-525AXSP02	-	-	-	-	1219.5	-	-	-	-	1206.1	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK550K8-425AXSP02	-	644.4	-	-	1121.1	-	645.8	-	-	1109.9	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S6ZK750K8-625AXSP02	-	-	-	-	1402.3	-	-	-	-	1387.7	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD15S6ZK750K8-525AXSP02	-	772.8	-	-	1330.2	-	774.7	-	-	1316.9	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD15S6ZK750K8-425AXSP02	-	700.1	-	-	1219.5	-	701.6	-	-	1208.6	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD15S1PB370K4-625AXSP16	-	97.7	-	-	163.3	-	97.4	-	-	161.3	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB370K4-525AXSP16	-	90.7	68.3	77.4	153.6	-	90.6	68.6	77.4	152.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB370K4-425AXSP16	-	84.8	63.5	72.2	145.4	-	84.8	63.8	72.3	143.9	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB550K4-625AXSP16	-	108.9	-	93.2	182.7	-	108.8	-	93.3	181	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB550K4-525AXSP16	-	100.8	75.8	85.9	171.6	-	100.8	76.2	86.1	170	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB550K4-425AXSP16	57.30	94	70.3	80.1	161.8	58.3	94	70.8	80.2	160.4	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB750K4-625AXSP16	-	116.8	88.3	99.8	196.6	-	116.9	89	100.2	195	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB750K4-525AXSP16	-	108.2	81.1	92.1	184.5	67.6	108.2	81.8	92.4	183.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB750K4-425AXSP12	-	95	-	80.3	167.7	-	95.9	-	81.2	166.9	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S1PB370K5-625AXSP16	-	97.7	-	-	163.3	-	97.4	-	-	161.3	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB370K5-525AXSP16	-	90.7	68.3	77.4	153.6	-	90.6	68.6	77.4	152.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB370K5-425AXSP16	-	84.8	63.5	72.2	145.4	-	84.8	63.8	72.3	143.9	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB550K5-625AXSP16	-	108.9	-	93.2	182.7	-	108.8	-	93.3	181	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB550K5-525AXSP16	-	100.8	75.8	85.9	171.6	-	100.8	76.2	86.1	170	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB550K5-425AXSP16	57.30	94	70.3	80.1	161.8	58.3	94	70.8	80.2	160.4	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB750K5-625AXSP16	-	116.8	88.3	99.8	196.6	-	116.9	89	100.2	195	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB750K5-525AXSP16	-	108.2	81.1	92.1	184.5	67.6	108.2	81.8	92.4	183.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB750K5-425AXSP12	-	95	-	80.3	167.7	-	95.9	-	81.2	166.9	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S1PB370C4-625AXSP16	-	101.5	-	86.9	170.1	-	101.5	-	87	168.2	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB370C4-525AXSP16	-	94.3	71	80.6	160.2	-	94.3	71.3	80.6	158.6	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB370C4-425AXSP16	-	88	66	75	151.2	-	88.1	66.3	75.1	149.8	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB550C4-625AXSP16	-	114.7	86.8	98.1	193	-	114.8	87.3	98.3	191	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB550C4-525AXSP16	-	106	79.6	90.3	180.9	-	106.1	80.1	90.5	179.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB550C4-425AXSP12	-	92.8	-	78.4	163.5	-	93.4	-	79.2	162.7	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S1PB750C4-625AXSP16	-	120.9	91.3	103.5	203.8	-	121.1	92.1	103.8	202.2	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB750C4-525AXSP16	68.70	112	84	95.4	191.3	70	112.1	84.6	95.7	190	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB750C4-425AXSP12	-	98.2	-	83	173.5	-	99.2	73.4	84	172.7	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S1PB370C5-625AXSP16	-	101.5	-	86.9	170.1	-	101.5	-	87	168.2	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB370C5-525AXSP16	-	94.3	71	80.6	160.2	-	94.3	71.3	80.6	158.6	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB370C5-425AXSP16	-	88	66	75	151.2	-	88.1	66.3	75.1	149.8	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB550C5-625AXSP16	-	114.7	86.8	98.1	193	-	114.8	87.3	98.3	191	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB550C5-525AXSP16	-	106	79.6	90.3	180.9	-	106.1	80.1	90.5	179.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB550C5-425AXSP12	-	92.8	-	78.4	163.5	-	93.4	-	79.2	162.7	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S1PB750C5-625AXSP16	-	120.9	91.3	103.5	203.8	-	121.1	92.1	103.8	202.2	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB750C5-525AXSP16	68.70	112	84	95.4	191.3	70	112.1	84.6	95.7	190	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB750C5-425AXSP12	-	98.2	-	83	173.5	-	99.2	73.4	84	172.7	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S1PB370K8-625AXSP16	-	97.7	-	-	163.3	-	97.4	-	-	161.3	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB370K8-525AXSP16	-	90.7	68.3	77.4	153.6	-	90.6	68.6	77.4	152.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB370K8-425AXSP16	-	84.8	63.5	72.2	145.4	-	84.8	63.8	72.3	143.9	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB550K8-625AXSP16	-	108.9	-	93.2	182.7	-	108.8	-	93.3	181	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB550K8-525AXSP16	-	100.8	75.8	85.9	171.6	-	100.8	76.2	86.1	170	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB550K8-425AXSP16	57.30	94	70.3	80.1	161.8	58.3	94	70.8	80.2	160.4	121	22.8	1-1/2"	97	15.1	1-1/2"	145	28.4	2"
EAW-VD15S1PB750K8-625AXSP16	-	116.8	88.3	99.8	196.6	-	116.9	89	100.2	195	182	22	2"	145	14.5	2"	218	30.9	2"
EAW-VD15S1PB750K8-525AXSP16	-	108.2	81.1	92.1	184.5	67.6	108.2	81.8	92.4	183.1	145	20.8	2"	116	16.2	1-1/2"	174	29.3	2"
EAW-VD15S1PB750K8-425AXSP12	-	95	-	80.3	167.7	-	95.9	-	81.2	166.9	157	16.5	2"	126	13.7	1-1/2"	189	23.2	2"
EAW-VD15S2PB370K4-625AXSP08	-	194.6	-	-	325.4	-	194.3	-	-	321.6	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB370K4-525AXSP08	-	184.2	-	157.5	312	-	184.1	-	157.4	308.7	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB370K4-425AXSP08	-	168.7	126.4	143.6	289.5	-	168.7	127	143.9	286.5	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB550K4-625AXSP08	-	216.9	-	185.6	364.5	-	216.8	-	185.8	360.6	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB550K4-525AXSP08	-	205.1	154.3	174.9	348.6	-	205	155.2	175.1	345.4	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB550K4-425AXSP08	114.00	187.4	139.8	159.3	322.6	116	187.4	140.8	159.7	319.4	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB750K4-625AXSP08	-	232.6	175.8	199.1	392.2	-	232.9	177.2	199.6	389	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB750K4-525AXSP08	-	220	165.2	187.5	375	-	220.3	166.5	188.1	372	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB750K4-425AXSP08	122.00	200.8	149.8	170.6	347	124.3	201.2	150.9	171.3	344.1	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB370K5-625AXSP08	-	194.6	-	-	325.4	-	194.3	-	-	321.6	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB370K5-525AXSP08	-	184.2	-	157.5	312	-	184.1	-	157.4	308.7	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB370K5-425AXSP08	-	168.7	126.4	143.6	289.5	-	168.7	127	143.9	286.5	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB550K5-625AXSP08	-	216.9	-	185.6	364.5	-	216.8	-	185.8	360.6	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB550K5-525AXSP08	-	205.1	154.3	174.9	348.6	-	205	155.2	175.1	345.4	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB550K5-425AXSP08	114.00	187.4	139.8	159.3	322.6	116	187.4	140.8	159.7	319.4	242	17.4	3"	194	14.4	2"	291	24.3	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S2PB750K5-625AXSP08	-	232.6	175.8	199.1	392.2	-	232.9	177.2	199.6	389	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB750K5-525AXSP08	-	220	165.2	187.5	375	-	220.3	166.5	188.1	372	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB750K5-425AXSP08	122.00	200.8	149.8	170.6	347	124.3	201.2	150.9	171.3	344.1	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB370C4-625AXSP08	-	202.3	-	173.3	338.9	-	202.2	-	173.5	335.3	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB370C4-525AXSP08	-	191.9	144.5	163.9	325.3	-	191.6	145.1	163.9	322	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB370C4-425AXSP08	-	175.2	131.2	149.3	301.2	-	175.3	131.9	149.4	298.3	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB550C4-625AXSP08	-	228.5	172.8	195.6	385.1	-	228.6	173.8	195.7	381.2	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB550C4-525AXSP08	-	215.6	162.1	183.9	367.7	-	215.6	163.1	184.2	363.8	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB550C4-425AXSP08	119.20	196	146.4	166.7	338.2	121.3	196.4	147.5	167	335.3	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB750C4-625AXSP08	-	240.9	181.8	206	406.7	-	241.3	183.4	206.6	403.4	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB750C4-525AXSP08	140.00	227.8	171.1	194.3	388.9	142.4	228.3	172.3	195.1	386.2	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB750C4-425AXSP08	126.10	207.8	155	176.7	359.2	128.3	208.3	156.2	177.1	356.7	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB370C5-625AXSP08	-	202.3	-	173.3	338.9	-	202.2	-	173.5	335.3	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB370C5-525AXSP08	-	191.9	144.5	163.9	325.3	-	191.6	145.1	163.9	322	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB370C5-425AXSP08	-	175.2	131.2	149.3	301.2	-	175.3	131.9	149.4	298.3	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB550C5-625AXSP08	-	228.5	172.8	195.6	385.1	-	228.6	173.8	195.7	381.2	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB550C5-525AXSP08	-	215.6	162.1	183.9	367.7	-	215.6	163.1	184.2	363.8	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB550C5-425AXSP08	119.20	196	146.4	166.7	338.2	121.3	196.4	147.5	167	335.3	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB750C5-625AXSP08	-	240.9	181.8	206	406.7	-	241.3	183.4	206.6	403.4	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB750C5-525AXSP08	140.00	227.8	171.1	194.3	388.9	142.4	228.3	172.3	195.1	386.2	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB750C5-425AXSP08	126.10	207.8	155	176.7	359.2	128.3	208.3	156.2	177.1	356.7	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB370K8-625AXSP08	-	194.6	-	-	325.4	-	194.3	-	-	321.6	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB370K8-525AXSP08	-	184.2	-	157.5	312	-	184.1	-	157.4	308.7	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB370K8-425AXSP08	-	168.7	126.4	143.6	289.5	-	168.7	127	143.9	286.5	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB550K8-625AXSP08	-	216.9	-	185.6	364.5	-	216.8	-	185.8	360.6	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB550K8-525AXSP08	-	205.1	154.3	174.9	348.6	-	205	155.2	175.1	345.4	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB550K8-425AXSP08	114.00	187.4	139.8	159.3	322.6	116	187.4	140.8	159.7	319.4	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S2PB750K8-625AXSP08	-	232.6	175.8	199.1	392.2	-	232.9	177.2	199.6	389	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD15S2PB750K8-525AXSP08	-	220	165.2	187.5	375	-	220.3	166.5	188.1	372	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD15S2PB750K8-425AXSP08	122.00	200.8	149.8	170.6	347	124.3	201.2	150.9	171.3	344.1	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD15S3PB370K4-625AXSP06	-	294.9	224.7	253.1	490.4	-	293.6	225.1	252.6	484.6	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB370K4-525AXSP06	-	277.9	210.4	238	468	-	277	210.9	237.5	462.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB370K4-425AXSP06	155.70	252.3	189.5	215.1	430.5	157.5	251.5	190.1	214.8	425.6	315	19.2	3"	252	12.7	3"	378	27	3"
EAW-VD15S3PB550K4-625AXSP06	-	328.7	250	281.9	549.4	-	327.8	250.5	281.4	542.9	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB550K4-525AXSP06	192.80	309.4	233.7	264.4	522.9	195.1	308.4	234.3	264.3	517.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB550K4-425AXSP04	-	266.5	-	224.8	468.9	-	268.3	-	227.3	466.5	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB750K4-625AXSP06	-	352.7	267.6	302	590.5	225	352.5	268.9	302.3	585.6	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB750K4-525AXSP06	206.20	331.9	250.4	283.5	562.5	209.1	331.4	251.4	283.5	557.3	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB750K4-425AXSP04	-	285.6	-	241.2	504.7	-	288.1	-	244	502.2	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB370K5-625AXSP06	-	294.9	224.7	253.1	490.4	-	293.6	225.1	252.6	484.6	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB370K5-525AXSP06	-	277.9	210.4	238	468	-	277	210.9	237.5	462.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB370K5-425AXSP06	155.70	252.3	189.5	215.1	430.5	157.5	251.5	190.1	214.8	425.6	315	19.2	3"	252	12.7	3"	378	27	3"
EAW-VD15S3PB550K5-625AXSP06	-	328.7	250	281.9	549.4	-	327.8	250.5	281.4	542.9	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB550K5-525AXSP06	192.80	309.4	233.7	264.4	522.9	195.1	308.4	234.3	264.3	517.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB550K5-425AXSP04	-	266.5	-	224.8	468.9	-	268.3	-	227.3	466.5	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB750K5-625AXSP06	-	352.7	267.6	302	590.5	225	352.5	268.9	302.3	585.6	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB750K5-525AXSP06	206.20	331.9	250.4	283.5	562.5	209.1	331.4	251.4	283.5	557.3	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB750K5-425AXSP04	-	285.6	-	241.2	504.7	-	288.1	-	244	502.2	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB370C4-625AXSP06	-	307	233.6	263.2	510.8	-	306	234	262.7	505.3	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB370C4-525AXSP06	-	289.4	218.8	247.3	488	-	288.6	219.4	247.3	482.4	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB370C4-425AXSP06	161.50	262	196.8	223.5	447.9	163.6	261.3	197.6	223.3	443	315	19.2	3"	252	12.7	3"	378	27	3"
EAW-VD15S3PB550C4-625AXSP06	-	346.4	263	296.8	579.8	-	345.6	264.1	296.9	573.8	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB550C4-525AXSP06	202.30	325.3	245.6	278	550.8	204.8	324.8	246.2	278	545.7	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB550C4-425AXSP04	-	278.9	-	235.3	492.1	-	280.8	-	238	489.6	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB750C4-625AXSP06	229.60	365.3	277.3	312.6	612.3	232.8	365.3	278.3	313	607.3	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB750C4-525AXSP06	213.40	343.8	259.3	293.4	583.4	216.3	343.5	260.2	294	578.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB750C4-425AXSP04	-	295.2	-	249.2	522.2	-	298	-	252.1	519.7	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB370C5-625AXSP06	-	307	233.6	263.2	510.8	-	306	234	262.7	505.3	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB370C5-525AXSP06	-	289.4	218.8	247.3	488	-	288.6	219.4	247.3	482.4	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB370C5-425AXSP06	161.50	262	196.8	223.5	447.9	163.6	261.3	197.6	223.3	443	315	19.2	3"	252	12.7	3"	378	27	3"
EAW-VD15S3PB550C5-625AXSP06	-	346.4	263	296.8	579.8	-	345.6	264.1	296.9	573.8	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB550C5-525AXSP06	202.30	325.3	245.6	278	550.8	204.8	324.8	246.2	278	545.7	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB550C5-425AXSP04	-	278.9	-	235.3	492.1	-	280.8	-	238	489.6	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB750C5-625AXSP06	229.60	365.3	277.3	312.6	612.3	232.8	365.3	278.3	313	607.3	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB750C5-525AXSP06	213.40	343.8	259.3	293.4	583.4	216.3	343.5	260.2	294	578.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB750C5-425AXSP04	-	295.2	-	249.2	522.2	-	298	-	252.1	519.7	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB370K8-625AXSP06	-	294.9	224.7	253.1	490.4	-	293.6	225.1	252.6	484.6	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB370K8-525AXSP06	-	277.9	210.4	238	468	-	277	210.9	237.5	462.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB370K8-425AXSP06	155.70	252.3	189.5	215.1	430.5	157.5	251.5	190.1	214.8	425.6	315	19.2	3"	252	12.7	3"	378	27	3"
EAW-VD15S3PB550K8-625AXSP06	-	328.7	250	281.9	549.4	-	327.8	250.5	281.4	542.9	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB550K8-525AXSP06	192.80	309.4	233.7	264.4	522.9	195.1	308.4	234.3	264.3	517.5	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB550K8-425AXSP04	-	266.5	-	224.8	468.9	-	268.3	-	227.3	466.5	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S3PB750K8-625AXSP06	-	352.7	267.6	302	590.5	225	352.5	268.9	302.3	585.6	484	21.7	3"	388	14.3	3"	581	26.4	4"
EAW-VD15S3PB750K8-525AXSP06	206.20	331.9	250.4	283.5	562.5	209.1	331.4	251.4	283.5	557.3	400	20.3	3"	320	13.4	3"	480	28.6	3"
EAW-VD15S3PB750K8-425AXSP04	-	285.6	-	241.2	504.7	-	288.1	-	244	502.2	484	15.9	3"	388	10.5	3"	581	18.2	4"
EAW-VD15S4PB370K4-625AXSP04	-	386.3	-	-	647	-	385.7	-	-	640.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB370K4-525AXSP04	-	365.4	-	312.1	620.1	-	365.2	-	312.5	613.6	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB370K4-425AXSP04	-	334.2	250	284.3	574.8	-	334.3	251.7	284.9	569.1	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB550K4-625AXSP04	-	430.9	-	368	724.6	-	430.3	-	368.6	717	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB550K4-525AXSP04	-	406.6	305.6	346.5	692.7	-	406.6	307.4	347.6	685.5	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB550K4-425AXSP04	225.20	371	277	315.2	639.4	229.3	371.2	278.6	316.5	634.1	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB750K4-625AXSP04	-	462.1	348.3	394.7	779.7	-	462.6	351.2	395.8	773.3	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB750K4-525AXSP04	-	436.6	327.1	372	745	-	436.7	329.7	373.2	739.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB750K4-425AXSP04	241.20	398.1	296.7	338.1	687.7	245.5	398.4	298.9	339.5	683	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB370K5-625AXSP04	-	386.3	-	-	647	-	385.7	-	-	640.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB370K5-525AXSP04	-	365.4	-	312.1	620.1	-	365.2	-	312.5	613.6	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB370K5-425AXSP04	-	334.2	250	284.3	574.8	-	334.3	251.7	284.9	569.1	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB550K5-625AXSP04	-	430.9	-	368	724.6	-	430.3	-	368.6	717	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB550K5-525AXSP04	-	406.6	305.6	346.5	692.7	-	406.6	307.4	347.6	685.5	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB550K5-425AXSP04	225.20	371	277	315.2	639.4	229.3	371.2	278.6	316.5	634.1	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB750K5-625AXSP04	-	462.1	348.3	394.7	779.7	-	462.6	351.2	395.8	773.3	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB750K5-525AXSP04	-	436.6	327.1	372	745	-	436.7	329.7	373.2	739.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB750K5-425AXSP04	241.20	398.1	296.7	338.1	687.7	245.5	398.4	298.9	339.5	683	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB370C4-625AXSP04	-	401.9	-	343.8	673.9	-	401.3	-	344.2	667.5	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB370C4-525AXSP04	-	380.4	286.3	324.7	646.5	-	380.5	288	325.3	639.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB370C4-425AXSP04	-	347.6	259.5	295.4	598	-	347.3	261.1	296.2	592.4	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB550C4-625AXSP04	-	453.9	342.4	387.9	764.7	-	453.6	344.6	388.7	757.8	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB550C4-525AXSP04	-	427.9	320.9	364.8	729.5	-	428	323	365.5	722.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB550C4-425AXSP04	235.60	388.6	289.9	330.2	671.4	239.8	388.8	291.6	331.1	664.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB750C4-625AXSP04	-	477.9	360.8	408.5	808.4	-	479.3	363.5	409.8	802	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB750C4-525AXSP04	-	452.2	338.8	384.9	772.6	282.4	452.6	341.8	386.5	767.2	606	17.2	4"	484	14.3	3"	727	24.2	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S4PB750C4-425AXSP04	249.20	411.2	306.7	349.4	712.9	253.8	412.3	308.8	351	707	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB370C5-625AXSP04	-	401.9	-	343.8	673.9	-	401.3	-	344.2	667.5	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB370C5-525AXSP04	-	380.4	286.3	324.7	646.5	-	380.5	288	325.3	639.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB370C5-425AXSP04	-	347.6	259.5	295.4	598	-	347.3	261.1	296.2	592.4	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB550C5-625AXSP04	-	453.9	342.4	387.9	764.7	-	453.6	344.6	388.7	757.8	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB550C5-525AXSP04	-	427.9	320.9	364.8	729.5	-	428	323	365.5	722.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB550C5-425AXSP04	235.60	388.6	289.9	330.2	671.4	239.8	388.8	291.6	331.1	664.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB750C5-625AXSP04	-	477.9	360.8	408.5	808.4	-	479.3	363.5	409.8	802	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB750C5-525AXSP04	-	452.2	338.8	384.9	772.6	282.4	452.6	341.8	386.5	767.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB750C5-425AXSP04	249.20	411.2	306.7	349.4	712.9	253.8	412.3	308.8	351	707	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB370K8-625AXSP04	-	386.3	-	-	647	-	385.7	-	-	640.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB370K8-525AXSP04	-	365.4	-	312.1	620.1	-	365.2	-	312.5	613.6	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB370K8-425AXSP04	-	334.2	250	284.3	574.8	-	334.3	251.7	284.9	569.1	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB550K8-625AXSP04	-	430.9	-	368	724.6	-	430.3	-	368.6	717	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB550K8-525AXSP04	-	406.6	305.6	346.5	692.7	-	406.6	307.4	347.6	685.5	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB550K8-425AXSP04	225.20	371	277	315.2	639.4	229.3	371.2	278.6	316.5	634.1	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PB750K8-625AXSP04	-	462.1	348.3	394.7	779.7	-	462.6	351.2	395.8	773.3	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S4PB750K8-525AXSP04	-	436.6	327.1	372	745	-	436.7	329.7	373.2	739.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S4PB750K8-425AXSP04	241.20	398.1	296.7	338.1	687.7	245.5	398.4	298.9	339.5	683	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S5PB370K4-625AXSP04	-	494	377.7	424.6	818.2	-	491.8	377.8	423.2	807.6	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB370K4-525AXSP04	295.60	468.4	355.6	400.8	784.9	297.8	466	355.7	399.9	774.7	606	20.7	4"	484	16.6	3"	727	29	4"
EAW-VD15S5PB370K4-425AXSP02	-	-	-	-	678.5	-	-	-	-	676.3	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB550K4-625AXSP04	350.40	550.8	420.3	473.1	916.7	353.4	549.1	420.5	471.6	905.9	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB550K4-525AXSP02	-	-	-	-	820.5	-	-	-	-	816.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550K4-425AXSP02	-	-	-	-	754.1	-	-	-	-	752	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB750K4-625AXSP04	375.30	590.9	450	507	985.4	379	589.8	451.3	506.6	975.9	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB750K4-525AXSP02	-	-	-	-	882.4	-	-	-	-	879.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750K4-425AXSP02	-	448.2	-	-	810.9	-	455.6	-	-	808.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB370K5-625AXSP04	-	494	377.7	424.6	818.2	-	491.8	377.8	423.2	807.6	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB370K5-525AXSP04	295.60	468.4	355.6	400.8	784.9	297.8	466	355.7	399.9	774.7	606	20.7	4"	484	16.6	3"	727	29	4"
EAW-VD15S5PB370K5-425AXSP02	-	-	-	-	678.5	-	-	-	-	676.3	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB550K5-625AXSP04	350.40	550.8	420.3	473.1	916.7	353.4	549.1	420.5	471.6	905.9	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB550K5-525AXSP02	-	-	-	-	820.5	-	-	-	-	816.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550K5-425AXSP02	-	-	-	-	754.1	-	-	-	-	752	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB750K5-625AXSP04	375.30	590.9	450	507	985.4	379	589.8	451.3	506.6	975.9	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB750K5-525AXSP02	-	-	-	-	882.4	-	-	-	-	879.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750K5-425AXSP02	-	448.2	-	-	810.9	-	455.6	-	-	808.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB370C4-625AXSP04	-	514.2	392.7	441.7	852.3	-	511.9	392.7	440.1	842.2	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB370C4-525AXSP04	307.30	487.2	369.9	417.1	817.5	309.7	485	370.2	415.7	808.1	606	20.7	4"	484	16.6	3"	727	29	4"
EAW-VD15S5PB370C4-425AXSP02	-	-	-	-	705.3	-	-	-	-	703.5	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB550C4-625AXSP04	369.00	580.5	442.3	498.2	967.5	371.9	578.3	442.7	496.8	957.5	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB550C4-525AXSP02	-	-	-	-	864.4	-	-	-	-	860.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550C4-425AXSP02	-	-	-	-	790.9	-	-	-	-	788.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB750C4-625AXSP04	388.20	612.1	465.6	524.8	1021.7	392.2	611.2	467.2	524.7	1013.5	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB750C4-525AXSP02	-	-	-	-	914.6	-	-	-	-	912.7	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750C4-425AXSP02	-	463.8	-	-	839.9	-	471.7	-	-	837.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB370C5-625AXSP04	-	514.2	392.7	441.7	852.3	-	511.9	392.7	440.1	842.2	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB370C5-525AXSP04	307.30	487.2	369.9	417.1	817.5	309.7	485	370.2	415.7	808.1	606	20.7	4"	484	16.6	3"	727	29	4"
EAW-VD15S5PB370C5-425AXSP02	-	-	-	-	705.3	-	-	-	-	703.5	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB550C5-625AXSP04	369.00	580.5	442.3	498.2	967.5	371.9	578.3	442.7	496.8	957.5	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB550C5-525AXSP02	-	-	-	-	864.4	-	-	-	-	860.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550C5-425AXSP02	-	-	-	-	790.9	-	-	-	-	788.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB750C5-625AXSP04	388.20	612.1	465.6	524.8	1021.7	392.2	611.2	467.2	524.7	1013.5	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB750C5-525AXSP02	-	-	-	-	914.6	-	-	-	-	912.7	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750C5-425AXSP02	-	463.8	-	-	839.9	-	471.7	-	-	837.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB370K8-625AXSP04	-	494	377.7	424.6	818.2	-	491.8	377.8	423.2	807.6	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB370K8-525AXSP04	295.60	468.4	355.6	400.8	784.9	297.8	466	355.7	399.9	774.7	606	20.7	4"	484	16.6	3"	727	29	4"
EAW-VD15S5PB370K8-425AXSP02	-	-	-	-	678.5	-	-	-	-	676.3	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB550K8-625AXSP04	350.40	550.8	420.3	473.1	916.7	353.4	549.1	420.5	471.6	905.9	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB550K8-525AXSP02	-	-	-	-	820.5	-	-	-	-	816.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB550K8-425AXSP02	-	-	-	-	754.1	-	-	-	-	752	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S5PB750K8-625AXSP04	375.30	590.9	450	507	985.4	379	589.8	451.3	506.6	975.9	727	21.7	4"	581	14.3	4"	872	30.4	4"
EAW-VD15S5PB750K8-525AXSP02	-	-	-	-	882.4	-	-	-	-	879.9	1211	11.4	(2) 4"	969	7.5	(2) 4"	1453	16.1	(2) 4"
EAW-VD15S5PB750K8-425AXSP02	-	448.2	-	-	810.9	-	455.6	-	-	808.7	969	10.6	(2) 4"	775	9.7	4"	1163	14.9	(2) 4"
EAW-VD15S6PB370K4-625AXSP02	-	-	-	-	941	-	-	-	-	933.6	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB370K4-525AXSP02	-	-	-	-	898.2	-	-	-	-	891.6	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB370K4-425AXSP02	-	470.5	-	-	829	-	474.5	-	-	823.6	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB550K4-625AXSP02	-	-	-	-	1051.7	-	-	-	-	1044.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB550K4-525AXSP02	-	574	-	-	1002.3	-	578.3	-	-	996.3	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB550K4-425AXSP02	-	521.7	-	-	922	-	526.5	-	-	917.7	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB750K4-625AXSP02	-	-	-	-	1130.9	-	-	-	-	1124.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB750K4-525AXSP02	-	615.4	-	-	1076.9	-	621.2	-	-	1072.1	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB750K4-425AXSP02	-	558.7	-	471.3	990.5	-	565	-	477.8	987.4	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB370K5-625AXSP02	-	-	-	-	941	-	-	-	-	933.6	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB370K5-525AXSP02	-	-	-	-	898.2	-	-	-	-	891.6	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB370K5-425AXSP02	-	470.5	-	-	829	-	474.5	-	-	823.6	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB550K5-625AXSP02	-	-	-	-	1051.7	-	-	-	-	1044.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB550K5-525AXSP02	-	574	-	-	1002.3	-	578.3	-	-	996.3	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB550K5-425AXSP02	-	521.7	-	-	922	-	526.5	-	-	917.7	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB750K5-625AXSP02	-	-	-	-	1130.9	-	-	-	-	1124.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB750K5-525AXSP02	-	615.4	-	-	1076.9	-	621.2	-	-	1072.1	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB750K5-425AXSP02	-	558.7	-	471.3	990.5	-	565	-	477.8	987.4	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB370C4-625AXSP02	-	-	-	-	979.8	-	-	-	-	973.3	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB370C4-525AXSP02	-	-	-	-	936.2	-	-	-	-	929.6	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB370C4-425AXSP02	-	488.9	-	-	861.9	-	492.6	-	-	856.8	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB550C4-625AXSP02	-	-	-	-	1110.7	-	-	-	-	1102.5	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB550C4-525AXSP02	-	603.4	-	-	1054.9	-	608.2	-	-	1048.7	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB550C4-425AXSP02	-	545.7	-	460.5	967.4	-	550.9	-	466.2	961.3	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB750C4-625AXSP02	-	676.3	-	-	1172.1	-	682.2	-	-	1166.2	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB750C4-525AXSP02	-	636.7	-	-	1116.4	-	643.3	-	-	1112.2	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB750C4-425AXSP02	-	578.4	-	487.4	1026.1	-	584.2	-	493.4	1021.5	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB370C5-625AXSP02	-	-	-	-	979.8	-	-	-	-	973.3	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB370C5-525AXSP02	-	-	-	-	936.2	-	-	-	-	929.6	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB370C5-425AXSP02	-	488.9	-	-	861.9	-	492.6	-	-	856.8	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB550C5-625AXSP02	-	-	-	-	1110.7	-	-	-	-	1102.5	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB550C5-525AXSP02	-	603.4	-	-	1054.9	-	608.2	-	-	1048.7	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB550C5-425AXSP02	-	545.7	-	460.5	967.4	-	550.9	-	466.2	961.3	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB750C5-625AXSP02	-	676.3	-	-	1172.1	-	682.2	-	-	1166.2	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB750C5-525AXSP02	-	636.7	-	-	1116.4	-	643.3	-	-	1112.2	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB750C5-425AXSP02	-	578.4	-	487.4	1026.1	-	584.2	-	493.4	1021.5	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB370K8-625AXSP02	-	-	-	-	941	-	-	-	-	933.6	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S6PB370K8-525AXSP02	-	-	-	-	898.2	-	-	-	-	891.6	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB370K8-425AXSP02	-	470.5	-	-	829	-	474.5	-	-	823.6	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB550K8-625AXSP02	-	-	-	-	1051.7	-	-	-	-	1044.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB550K8-525AXSP02	-	574	-	-	1002.3	-	578.3	-	-	996.3	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB550K8-425AXSP02	-	521.7	-	-	922	-	526.5	-	-	917.7	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S6PB750K8-625AXSP02	-	-	-	-	1130.9	-	-	-	-	1124.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD15S6PB750K8-525AXSP02	-	615.4	-	-	1076.9	-	621.2	-	-	1072.1	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD15S6PB750K8-425AXSP02	-	558.7	-	471.3	990.5	-	565	-	477.8	987.4	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD15S1PK370K4-625AXSP16	-	104.1	-	89.3	172.5	-	103.6	-	89.1	170.2	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK370K4-525AXSP16	-	96.7	73.2	82.8	162.6	-	96.3	73.3	82.5	160.7	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK370K4-425AXSP16	-	90.2	68	77	153.5	56.5	89.9	68	76.8	151.7	121	24.4	1-1/2"	97	16.1	1-1/2"	145	30.5	2"
EAW-VD15S1PK550K4-625AXSP16	-	116.6	88.7	99.9	194	-	116.1	88.9	99.8	191.7	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK550K4-525AXSP16	67.20	108	81.5	92.3	182.3	68.1	107.7	81.7	92.2	180.2	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK550K4-425AXSP12	-	95.2	-	80.7	166	-	95.6	-	81.2	164.6	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK750K4-625AXSP16	-	125.6	95.5	107.7	209.9	-	125.2	95.7	107.5	207.5	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK750K4-525AXSP12	-	111.8	-	95	193	-	112.3	-	95.6	191.6	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK750K4-425AXSP12	-	102.6	76	87	179.1	-	103.1	76.8	87.6	177.9	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK370K5-625AXSP16	-	104.1	-	89.3	172.5	-	103.6	-	89.1	170.2	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK370K5-525AXSP16	-	96.7	73.2	82.8	162.6	-	96.3	73.3	82.5	160.7	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK370K5-425AXSP16	-	90.2	68	77	153.5	56.5	89.9	68	76.8	151.7	121	24.4	1-1/2"	97	16.1	1-1/2"	145	30.5	2"
EAW-VD15S1PK550K5-625AXSP16	-	116.6	88.7	99.9	194	-	116.1	88.9	99.8	191.7	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK550K5-525AXSP16	67.20	108	81.5	92.3	182.3	68.1	107.7	81.7	92.2	180.2	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK550K5-425AXSP12	-	95.2	-	80.7	166	-	95.6	-	81.2	164.6	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK750K5-625AXSP16	-	125.6	95.5	107.7	209.9	-	125.2	95.7	107.5	207.5	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK750K5-525AXSP12	-	111.8	-	95	193	-	112.3	-	95.6	191.6	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK750K5-425AXSP12	-	102.6	76	87	179.1	-	103.1	76.8	87.6	177.9	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK370C4-625AXSP16	-	108.6	-	93.1	180.3	-	108	-	92.8	178	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK370C4-525AXSP16	-	100.7	76.2	86.1	169.6	-	100.3	76.3	86	167.5	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK370C4-425AXSP16	58.00	93.9	70.7	80.1	159.8	58.7	93.4	70.7	79.9	157.9	121	24.4	1-1/2"	97	16.1	1-1/2"	145	30.5	2"
EAW-VD15S1PK550C4-625AXSP16	-	123	93.4	105.3	205.2	-	122.5	93.6	105.2	202.8	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK550C4-525AXSP12	-	109.2	-	92.7	188.2	-	109.4	-	93.2	186.5	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK550C4-425AXSP12	-	99.6	73.7	84.5	173.9	-	99.9	74.6	84.9	172.4	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK750C4-625AXSP16	-	130.5	99.1	111.6	218.3	-	130.2	99.4	111.7	215.8	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK750C4-525AXSP12	-	115.9	-	98.4	200.4	-	116.4	-	99.2	199	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK750C4-425AXSP12	-	106.1	78.4	89.9	185.4	-	106.6	79.3	90.4	184.2	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK370C5-625AXSP16	-	108.6	-	93.1	180.3	-	108	-	92.8	178	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK370C5-525AXSP16	-	100.7	76.2	86.1	169.6	-	100.3	76.3	86	167.5	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK370C5-425AXSP16	58.00	93.9	70.7	80.1	159.8	58.7	93.4	70.7	79.9	157.9	121	24.4	1-1/2"	97	16.1	1-1/2"	145	30.5	2"
EAW-VD15S1PK550C5-625AXSP16	-	123	93.4	105.3	205.2	-	122.5	93.6	105.2	202.8	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK550C5-525AXSP12	-	109.2	-	92.7	188.2	-	109.4	-	93.2	186.5	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK550C5-425AXSP12	-	99.6	73.7	84.5	173.9	-	99.9	74.6	84.9	172.4	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK750C5-625AXSP16	-	130.5	99.1	111.6	218.3	-	130.2	99.4	111.7	215.8	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK750C5-525AXSP12	-	115.9	-	98.4	200.4	-	116.4	-	99.2	199	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK750C5-425AXSP12	-	106.1	78.4	89.9	185.4	-	106.6	79.3	90.4	184.2	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK370K8-625AXSP16	-	104.1	-	89.3	172.5	-	103.6	-	89.1	170.2	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK370K8-525AXSP16	-	96.7	73.2	82.8	162.6	-	96.3	73.3	82.5	160.7	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK370K8-425AXSP16	-	90.2	68	77	153.5	56.5	89.9	68	76.8	151.7	121	24.4	1-1/2"	97	16.1	1-1/2"	145	30.5	2"
EAW-VD15S1PK550K8-625AXSP16	-	116.6	88.7	99.9	194	-	116.1	88.9	99.8	191.7	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK550K8-525AXSP16	67.20	108	81.5	92.3	182.3	68.1	107.7	81.7	92.2	180.2	145	22.4	2"	116	17.2	1-1/2"	174	31.4	2"
EAW-VD15S1PK550K8-425AXSP12	-	95.2	-	80.7	166	-	95.6	-	81.2	164.6	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S1PK750K8-625AXSP16	-	125.6	95.5	107.7	209.9	-	125.2	95.7	107.5	207.5	182	23.5	2"	145	15.5	2"	218	33	2"
EAW-VD15S1PK750K8-525AXSP12	-	111.8	-	95	193	-	112.3	-	95.6	191.6	194	18.9	2"	155	12.4	2"	232	26.5	2"
EAW-VD15S1PK750K8-425AXSP12	-	102.6	76	87	179.1	-	103.1	76.8	87.6	177.9	157	17.6	2"	126	14.5	1-1/2"	189	24.8	2"
EAW-VD15S2PK370K4-625AXSP08	-	207.5	-	178	344.2	-	206.3	-	177.4	339.7	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK370K4-525AXSP08	-	196.4	148.9	168.2	330.1	-	195.8	149	167.7	325.8	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK370K4-425AXSP08	-	179.6	135.3	153.2	305.7	112.4	179	135.4	153	302.2	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK550K4-625AXSP08	-	232.2	176.7	199.1	387.1	-	231.3	177	198.8	382.5	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK550K4-525AXSP08	-	219.4	165.9	187.7	370.3	-	218.7	166.3	187.4	366	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK550K4-425AXSP08	123.30	200.2	150.5	170.6	342.3	124.8	199.8	150.7	170.5	338.2	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK750K4-625AXSP08	-	250.2	190.1	214.5	418.3	-	249.5	190.6	214.1	413.9	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK750K4-525AXSP08	147.20	236.4	178.5	201.9	400.1	149	236	179.2	201.9	396	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK750K4-425AXSP06	-	203.9	150.6	172.6	356.6	-	204.9	152.7	173.9	353.7	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S2PK370K5-625AXSP08	-	207.5	-	178	344.2	-	206.3	-	177.4	339.7	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK370K5-525AXSP08	-	196.4	148.9	168.2	330.1	-	195.8	149	167.7	325.8	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK370K5-425AXSP08	-	179.6	135.3	153.2	305.7	112.4	179	135.4	153	302.2	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK550K5-625AXSP08	-	232.2	176.7	199.1	387.1	-	231.3	177	198.8	382.5	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK550K5-525AXSP08	-	219.4	165.9	187.7	370.3	-	218.7	166.3	187.4	366	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK550K5-425AXSP08	123.30	200.2	150.5	170.6	342.3	124.8	199.8	150.7	170.5	338.2	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK750K5-625AXSP08	-	250.2	190.1	214.5	418.3	-	249.5	190.6	214.1	413.9	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK750K5-525AXSP08	147.20	236.4	178.5	201.9	400.1	149	236	179.2	201.9	396	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK750K5-425AXSP06	-	203.9	150.6	172.6	356.6	-	204.9	152.7	173.9	353.7	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S2PK370C4-625AXSP08	-	216.4	-	185.7	359.7	-	215.5	-	185.2	355.1	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK370C4-525AXSP08	-	204.8	155	175.2	344.4	-	203.9	155.1	174.7	340.1	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK370C4-425AXSP08	115.40	186.9	140.6	159.3	318.6	116.7	186.3	140.7	159.1	314.6	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK550C4-625AXSP08	-	245	186.3	210.1	409.4	-	244.3	186.5	209.5	404.6	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK550C4-525AXSP08	143.90	230.6	174.3	197.1	390.1	145.6	229.9	174.7	196.8	385.4	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK550C4-425AXSP06	-	197.9	146.6	167.7	345.6	-	198.8	148.2	168.9	342.7	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S2PK750C4-625AXSP08	-	259.9	197.3	222.6	435	-	259.4	197.9	222.5	430.7	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK750C4-525AXSP08	152.40	245.2	184.9	209.3	415.7	154.5	244.9	185.7	209.3	411.4	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK750C4-425AXSP06	-	210.6	155.7	178.5	368.6	-	211.7	157.7	179.8	366.1	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S2PK370C5-625AXSP08	-	216.4	-	185.7	359.7	-	215.5	-	185.2	355.1	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK370C5-525AXSP08	-	204.8	155	175.2	344.4	-	203.9	155.1	174.7	340.1	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK370C5-425AXSP08	115.40	186.9	140.6	159.3	318.6	116.7	186.3	140.7	159.1	314.6	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK550C5-625AXSP08	-	245	186.3	210.1	409.4	-	244.3	186.5	209.5	404.6	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK550C5-525AXSP08	143.90	230.6	174.3	197.1	390.1	145.6	229.9	174.7	196.8	385.4	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK550C5-425AXSP06	-	197.9	146.6	167.7	345.6	-	198.8	148.2	168.9	342.7	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S2PK750C5-625AXSP08	-	259.9	197.3	222.6	435	-	259.4	197.9	222.5	430.7	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK750C5-525AXSP08	152.40	245.2	184.9	209.3	415.7	154.5	244.9	185.7	209.3	411.4	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK750C5-425AXSP06	-	210.6	155.7	178.5	368.6	-	211.7	157.7	179.8	366.1	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S2PK370K8-625AXSP08	-	207.5	-	178	344.2	-	206.3	-	177.4	339.7	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK370K8-525AXSP08	-	196.4	148.9	168.2	330.1	-	195.8	149	167.7	325.8	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK370K8-425AXSP08	-	179.6	135.3	153.2	305.7	112.4	179	135.4	153	302.2	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK550K8-625AXSP08	-	232.2	176.7	199.1	387.1	-	231.3	177	198.8	382.5	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK550K8-525AXSP08	-	219.4	165.9	187.7	370.3	-	218.7	166.3	187.4	366	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK550K8-425AXSP08	123.30	200.2	150.5	170.6	342.3	124.8	199.8	150.7	170.5	338.2	242	18.9	3"	194	15.4	2"	291	26.5	3"
EAW-VD15S2PK750K8-625AXSP08	-	250.2	190.1	214.5	418.3	-	249.5	190.6	214.1	413.9	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD15S2PK750K8-525AXSP08	147.20	236.4	178.5	201.9	400.1	149	236	179.2	201.9	396	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD15S2PK750K8-425AXSP06	-	203.9	150.6	172.6	356.6	-	204.9	152.7	173.9	353.7	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD15S3PK370K4-625AXSP06	-	314	240.5	269.8	518	-	311.8	239.9	268.5	511.3	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK370K4-525AXSP06	187.20	295.9	225.1	253.8	495.1	188.6	294.4	224.8	252.6	488.1	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK370K4-425AXSP04	-	257.3	-	-	446.5	-	257.9	-	-	442.7	484	17.1	3"	388	11.2	3"	581	19.8	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PK550K4-625AXSP06	224.30	351.5	268.4	301.9	582.7	226.1	349.5	268.1	300.5	575.1	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK550K4-525AXSP06	208.20	330.5	250.8	283.3	554.8	209.9	328.9	250.9	282.3	548.3	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK550K4-425AXSP04	-	286.1	-	242.6	499.4	-	287.3	-	244.1	495.1	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK750K4-625AXSP06	241.20	378.7	288.9	325.3	629.7	243	377.1	289.1	324.3	623.1	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK750K4-525AXSP04	-	338.6	-	287.8	584.5	-	340.4	-	289.5	580.2	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK750K4-425AXSP04	-	308.5	227.9	261.4	539	-	309.9	230.8	263.2	535.3	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK370K5-625AXSP06	-	314	240.5	269.8	518	-	311.8	239.9	268.5	511.3	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK370K5-525AXSP06	187.20	295.9	225.1	253.8	495.1	188.6	294.4	224.8	252.6	488.1	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK370K5-425AXSP04	-	257.3	-	-	446.5	-	257.9	-	-	442.7	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK550K5-625AXSP06	224.30	351.5	268.4	301.9	582.7	226.1	349.5	268.1	300.5	575.1	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK550K5-525AXSP06	208.20	330.5	250.8	283.3	554.8	209.9	328.9	250.9	282.3	548.3	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK550K5-425AXSP04	-	286.1	-	242.6	499.4	-	287.3	-	244.1	495.1	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK750K5-625AXSP06	241.20	378.7	288.9	325.3	629.7	243	377.1	289.1	324.3	623.1	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK750K5-525AXSP04	-	338.6	-	287.8	584.5	-	340.4	-	289.5	580.2	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK750K5-425AXSP04	-	308.5	227.9	261.4	539	-	309.9	230.8	263.2	535.3	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK370C4-625AXSP06	-	327.5	250.5	281.6	541.4	-	325.7	250	280	533.9	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK370C4-525AXSP06	194.80	308.4	234.3	264.4	516	196.3	306.6	234.1	263.2	509.5	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK370C4-425AXSP04	-	267.2	-	226.6	465.2	-	268.3	-	228	460.8	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK550C4-625AXSP06	236.10	370.8	283.1	318.2	616.2	238.1	368.8	282.9	317.2	608.3	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK550C4-525AXSP04	-	330.5	-	280.7	569.9	-	331.7	-	282.3	564.8	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK550C4-425AXSP04	-	299.5	-	253.5	523.1	-	300.8	-	255.2	518.7	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK750C4-625AXSP06	249.80	393.4	299.8	337.2	654.8	252.2	392.1	299.8	336.5	647.5	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK750C4-525AXSP04	-	351	-	298.1	607	-	353	-	300.4	602.6	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK750C4-425AXSP04	-	318.7	235.5	269.7	558.1	-	320.3	238.5	271.7	554.3	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK370C5-625AXSP06	-	327.5	250.5	281.6	541.4	-	325.7	250	280	533.9	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK370C5-525AXSP06	194.80	308.4	234.3	264.4	516	196.3	306.6	234.1	263.2	509.5	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK370C5-425AXSP04	-	267.2	-	226.6	465.2	-	268.3	-	228	460.8	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK550C5-625AXSP06	236.10	370.8	283.1	318.2	616.2	238.1	368.8	282.9	317.2	608.3	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK550C5-525AXSP04	-	330.5	-	280.7	569.9	-	331.7	-	282.3	564.8	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK550C5-425AXSP04	-	299.5	-	253.5	523.1	-	300.8	-	255.2	518.7	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK750C5-625AXSP06	249.80	393.4	299.8	337.2	654.8	252.2	392.1	299.8	336.5	647.5	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK750C5-525AXSP04	-	351	-	298.1	607	-	353	-	300.4	602.6	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK750C5-425AXSP04	-	318.7	235.5	269.7	558.1	-	320.3	238.5	271.7	554.3	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK370K8-625AXSP06	-	314	240.5	269.8	518	-	311.8	239.9	268.5	511.3	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK370K8-525AXSP06	187.20	295.9	225.1	253.8	495.1	188.6	294.4	224.8	252.6	488.1	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK370K8-425AXSP04	-	257.3	-	-	446.5	-	257.9	-	-	442.7	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK550K8-625AXSP06	224.30	351.5	268.4	301.9	582.7	226.1	349.5	268.1	300.5	575.1	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK550K8-525AXSP06	208.20	330.5	250.8	283.3	554.8	209.9	328.9	250.9	282.3	548.3	400	22.1	3"	320	14.6	3"	480	31	3"
EAW-VD15S3PK550K8-425AXSP04	-	286.1	-	242.6	499.4	-	287.3	-	244.1	495.1	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S3PK750K8-625AXSP06	241.20	378.7	288.9	325.3	629.7	243	377.1	289.1	324.3	623.1	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD15S3PK750K8-525AXSP04	-	338.6	-	287.8	584.5	-	340.4	-	289.5	580.2	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD15S3PK750K8-425AXSP04	-	308.5	227.9	261.4	539	-	309.9	230.8	263.2	535.3	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD15S4PK370K4-625AXSP04	-	411.9	-	353.6	684.4	-	410.2	-	352.5	675.6	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK370K4-525AXSP04	-	389.7	295.1	333.5	656	-	388.4	295.8	332.9	647.6	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK370K4-425AXSP04	-	356.4	267.7	304	607.2	-	355.2	268.5	303.4	600.2	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK550K4-625AXSP04	-	460.9	350.3	395.4	769.6	-	459.6	351.1	394.3	760.6	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK550K4-525AXSP04	-	435	329.1	372	735	-	434.3	330	372	727.4	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK550K4-425AXSP04	244.30	397.1	297.8	338.2	678.6	247.3	395.8	298.7	338.2	671.7	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK750K4-625AXSP04	-	497.1	376.9	425.3	831.7	-	495.8	378.4	425.3	823	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK750K4-525AXSP04	291.40	468.7	353.5	400.7	794	295	468	355	400.7	786.8	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK750K4-425AXSP02	-	-	-	-	677	-	-	-	-	677.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD15S4PK370K5-625AXSP04	-	411.9	-	353.6	684.4	-	410.2	-	352.5	675.6	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK370K5-525AXSP04	-	389.7	295.1	333.5	656	-	388.4	295.8	332.9	647.6	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK370K5-425AXSP04	-	356.4	267.7	304	607.2	-	355.2	268.5	303.4	600.2	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK550K5-625AXSP04	-	460.9	350.3	395.4	769.6	-	459.6	351.1	394.3	760.6	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK550K5-525AXSP04	-	435	329.1	372	735	-	434.3	330	372	727.4	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK550K5-425AXSP04	244.30	397.1	297.8	338.2	678.6	247.3	395.8	298.7	338.2	671.7	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK750K5-625AXSP04	-	497.1	376.9	425.3	831.7	-	495.8	378.4	425.3	823	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK750K5-525AXSP04	291.40	468.7	353.5	400.7	794	295	468	355	400.7	786.8	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK750K5-425AXSP02	-	-	-	-	677	-	-	-	-	677.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD15S4PK370C4-625AXSP04	-	430.1	-	368.5	715.2	-	427.9	-	367.5	706.2	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK370C4-525AXSP04	-	406.1	307.1	347.3	684.6	-	405	308	346.8	676	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK370C4-425AXSP04	228.20	370.3	278.2	316	631.9	231	369.2	279.1	315.5	624.8	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK550C4-625AXSP04	-	486.1	369.4	416.6	813.9	-	484.8	370.3	416.1	804.4	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK550C4-525AXSP04	284.80	457.3	345.3	390.6	774.1	288.3	456.5	346.2	390.6	765.8	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK550C4-425AXSP04	255.00	415.2	311.2	353.7	711.2	258.2	413.8	312.2	353.2	703.8	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK750C4-625AXSP04	-	515.6	391	441.4	864.7	-	514.7	392.4	441.8	856.2	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK750C4-525AXSP04	301.50	486.1	366.7	415.3	824.7	305.9	485.5	367.8	415.4	817.4	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK750C4-425AXSP02	-	-	-	-	701.5	-	-	-	-	700.9	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD15S4PK370C5-625AXSP04	-	430.1	-	368.5	715.2	-	427.9	-	367.5	706.2	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK370C5-525AXSP04	-	406.1	307.1	347.3	684.6	-	405	308	346.8	676	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK370C5-425AXSP04	228.20	370.3	278.2	316	631.9	231	369.2	279.1	315.5	624.8	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK550C5-625AXSP04	-	486.1	369.4	416.6	813.9	-	484.8	370.3	416.1	804.4	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK550C5-525AXSP04	284.80	457.3	345.3	390.6	774.1	288.3	456.5	346.2	390.6	765.8	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK550C5-425AXSP04	255.00	415.2	311.2	353.7	711.2	258.2	413.8	312.2	353.2	703.8	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK750C5-625AXSP04	-	515.6	391	441.4	864.7	-	514.7	392.4	441.8	856.2	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK750C5-525AXSP04	301.50	486.1	366.7	415.3	824.7	305.9	485.5	367.8	415.4	817.4	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK750C5-425AXSP02	-	-	-	-	701.5	-	-	-	-	700.9	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD15S4PK370K8-625AXSP04	-	411.9	-	353.6	684.4	-	410.2	-	352.5	675.6	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK370K8-525AXSP04	-	389.7	295.1	333.5	656	-	388.4	295.8	332.9	647.6	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK370K8-425AXSP04	-	356.4	267.7	304	607.2	-	355.2	268.5	303.4	600.2	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK550K8-625AXSP04	-	460.9	350.3	395.4	769.6	-	459.6	351.1	394.3	760.6	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK550K8-525AXSP04	-	435	329.1	372	735	-	434.3	330	372	727.4	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK550K8-425AXSP04	244.30	397.1	297.8	338.2	678.6	247.3	395.8	298.7	338.2	671.7	484	20.9	3"	388	13.8	3"	581	25.2	4"
EAW-VD15S4PK750K8-625AXSP04	-	497.1	376.9	425.3	831.7	-	495.8	378.4	425.3	823	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD15S4PK750K8-525AXSP04	291.40	468.7	353.5	400.7	794	295	468	355	400.7	786.8	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD15S4PK750K8-425AXSP02	-	-	-	-	677	-	-	-	-	677.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD15S5PK370K4-625AXSP04	339.20	525.9	403.5	452.6	864.3	340.8	521.6	401.9	449.3	852.2	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK370K4-525AXSP02	-	-	-	-	782.3	-	-	-	-	776.7	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK370K4-425AXSP02	-	-	-	-	720.9	-	-	-	-	716.3	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK550K4-625AXSP04	378.20	588.8	450.4	505.8	972.2	380.1	584.7	449.4	503.5	959.7	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK550K4-525AXSP02	-	-	-	-	876.3	-	-	-	-	870.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK550K4-425AXSP02	-	452.6	-	-	805.2	-	457.6	-	-	800.1	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK750K4-625AXSP02	-	-	-	-	993.3	-	-	-	-	988.4	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK750K4-525AXSP02	-	-	-	-	945.5	-	-	-	-	940.2	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK750K4-425AXSP02	-	487.1	-	-	868.2	-	492.8	-	-	864.2	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK370K5-625AXSP04	339.20	525.9	403.5	452.6	864.3	340.8	521.6	401.9	449.3	852.2	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK370K5-525AXSP02	-	-	-	-	782.3	-	-	-	-	776.7	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK370K5-425AXSP02	-	-	-	-	720.9	-	-	-	-	716.3	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK550K5-625AXSP04	378.20	588.8	450.4	505.8	972.2	380.1	584.7	449.4	503.5	959.7	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK550K5-525AXSP02	-	-	-	-	876.3	-	-	-	-	870.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S5PK550K5-425AXSP02	-	452.6	-	-	805.2	-	457.6	-	-	800.1	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK750K5-625AXSP02	-	-	-	-	993.3	-	-	-	-	988.4	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK750K5-525AXSP02	-	-	-	-	945.5	-	-	-	-	940.2	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK750K5-425AXSP02	-	487.1	-	-	868.2	-	492.8	-	-	864.2	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK370C4-625AXSP04	353.20	548.5	420.4	471.8	903.3	355.1	544.2	419.5	469.1	890.8	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK370C4-525AXSP02	-	-	-	-	815.9	-	-	-	-	810.3	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK370C4-425AXSP02	-	-	-	-	749.7	-	-	-	-	745.1	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK550C4-625AXSP02	-	-	-	-	972.3	-	-	-	-	965.1	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK550C4-525AXSP02	-	-	-	-	922.1	-	-	-	-	915.4	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK550C4-425AXSP02	-	473.2	-	-	843	-	477.7	-	-	838.9	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK750C4-625AXSP02	-	-	-	-	1032.3	-	-	-	-	1026.6	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK750C4-525AXSP02	-	-	-	-	981.5	-	562.7	-	-	976.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK750C4-425AXSP02	-	503.8	-	-	898.5	-	508.9	-	-	894.4	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK370C5-625AXSP04	353.20	548.5	420.4	471.8	903.3	355.1	544.2	419.5	469.1	890.8	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK370C5-525AXSP02	-	-	-	-	815.9	-	-	-	-	810.3	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK370C5-425AXSP02	-	-	-	-	749.7	-	-	-	-	745.1	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK550C5-625AXSP02	-	-	-	-	972.3	-	-	-	-	965.1	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK550C5-525AXSP02	-	-	-	-	922.1	-	-	-	-	915.4	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK550C5-425AXSP02	-	473.2	-	-	843	-	477.7	-	-	838.9	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK750C5-625AXSP02	-	-	-	-	1032.3	-	-	-	-	1026.6	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK750C5-525AXSP02	-	-	-	-	981.5	-	562.7	-	-	976.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK750C5-425AXSP02	-	503.8	-	-	898.5	-	508.9	-	-	894.4	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK370K8-625AXSP04	339.20	525.9	403.5	452.6	864.3	340.8	521.6	401.9	449.3	852.2	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK370K8-525AXSP02	-	-	-	-	782.3	-	-	-	-	776.7	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK370K8-425AXSP02	-	-	-	-	720.9	-	-	-	-	716.3	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK550K8-625AXSP04	378.20	588.8	450.4	505.8	972.2	380.1	584.7	449.4	503.5	959.7	727	23.6	4"	581	15.5	4"	872	33.1	4"
EAW-VD15S5PK550K8-525AXSP02	-	-	-	-	876.3	-	-	-	-	870.1	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK550K8-425AXSP02	-	452.6	-	-	805.2	-	457.6	-	-	800.1	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S5PK750K8-625AXSP02	-	-	-	-	993.3	-	-	-	-	988.4	1453	13.4	(2) 4"	1163	8.8	(2) 4"	1744	18.8	(2) 4"
EAW-VD15S5PK750K8-525AXSP02	-	-	-	-	945.5	-	-	-	-	940.2	1211	12.4	(2) 4"	969	8.2	(2) 4"	1453	17.4	(2) 4"
EAW-VD15S5PK750K8-425AXSP02	-	487.1	-	-	868.2	-	492.8	-	-	864.2	969	11.6	(2) 4"	775	10.4	4"	1163	16.3	(2) 4"
EAW-VD15S6PK370K4-625AXSP02	-	-	-	-	998.2	-	-	-	-	988	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK370K4-525AXSP02	-	-	-	-	953.5	-	-	-	-	944	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK370K4-425AXSP02	-	504.6	-	-	879	-	506.8	-	-	871.9	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK550K4-625AXSP02	-	-	-	-	1120.4	-	-	-	-	1110.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK550K4-525AXSP02	-	618	-	-	1067.1	-	620.5	-	-	1058	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK550K4-425AXSP02	-	561.6	-	475.4	982.5	-	564.3	-	478.8	974.5	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK750K4-625AXSP02	-	707	-	-	1210	-	709.8	-	-	1200.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK750K4-525AXSP02	-	664.8	-	564.4	1151.8	-	668.7	-	568.9	1143.5	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK750K4-425AXSP02	-	604	-	510.9	1059.8	-	608.3	451.8	515.8	1053	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK370K5-625AXSP02	-	-	-	-	998.2	-	-	-	-	988	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK370K5-525AXSP02	-	-	-	-	953.5	-	-	-	-	944	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK370K5-425AXSP02	-	504.6	-	-	879	-	506.8	-	-	871.9	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK550K5-625AXSP02	-	-	-	-	1120.4	-	-	-	-	1110.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK550K5-525AXSP02	-	618	-	-	1067.1	-	620.5	-	-	1058	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK550K5-425AXSP02	-	561.6	-	475.4	982.5	-	564.3	-	478.8	974.5	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK750K5-625AXSP02	-	707	-	-	1210	-	709.8	-	-	1200.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK750K5-525AXSP02	-	664.8	-	564.4	1151.8	-	668.7	-	568.9	1143.5	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK750K5-425AXSP02	-	604	-	510.9	1059.8	-	608.3	451.8	515.8	1053	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK370C4-625AXSP02	-	-	-	-	1042.9	-	-	-	-	1032.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK370C4-525AXSP02	-	576.9	-	-	993.3	-	579.2	-	-	985	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK370C4-425AXSP02	-	524.6	-	-	914.4	-	526.3	-	-	907.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK550C4-625AXSP02	-	692.6	-	-	1184.3	-	694.4	-	-	1173.8	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK550C4-525AXSP02	-	649	-	-	1123.2	-	651.7	-	-	1113.3	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK550C4-425AXSP02	-	587.5	-	496.6	1029	-	589.4	-	500.3	1020.4	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK750C4-625AXSP02	-	734	-	-	1257.6	-	737.5	-	-	1248.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK750C4-525AXSP02	-	689.1	-	584.4	1195.9	-	693.3	-	589.3	1187.4	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK750C4-425AXSP02	-	625	460.5	528.1	1097.1	-	628.4	466.7	533.3	1090	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK370C5-625AXSP02	-	-	-	-	1042.9	-	-	-	-	1032.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK370C5-525AXSP02	-	576.9	-	-	993.3	-	579.2	-	-	985	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK370C5-425AXSP02	-	524.6	-	-	914.4	-	526.3	-	-	907.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK550C5-625AXSP02	-	692.6	-	-	1184.3	-	694.4	-	-	1173.8	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK550C5-525AXSP02	-	649	-	-	1123.2	-	651.7	-	-	1113.3	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK550C5-425AXSP02	-	587.5	-	496.6	1029	-	589.4	-	500.3	1020.4	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK750C5-625AXSP02	-	734	-	-	1257.6	-	737.5	-	-	1248.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK750C5-525AXSP02	-	689.1	-	584.4	1195.9	-	693.3	-	589.3	1187.4	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK750C5-425AXSP02	-	625	460.5	528.1	1097.1	-	628.4	466.7	533.3	1090	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK370K8-625AXSP02	-	-	-	-	998.2	-	-	-	-	988	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK370K8-525AXSP02	-	-	-	-	953.5	-	-	-	-	944	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK370K8-425AXSP02	-	504.6	-	-	879	-	506.8	-	-	871.9	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK550K8-625AXSP02	-	-	-	-	1120.4	-	-	-	-	1110.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK550K8-525AXSP02	-	618	-	-	1067.1	-	620.5	-	-	1058	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK550K8-425AXSP02	-	561.6	-	475.4	982.5	-	564.3	-	478.8	974.5	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S6PK750K8-625AXSP02	-	707	-	-	1210	-	709.8	-	-	1200.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S6PK750K8-525AXSP02	-	664.8	-	564.4	1151.8	-	668.7	-	568.9	1143.5	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S6PK750K8-425AXSP02	-	604	-	510.9	1059.8	-	608.3	451.8	515.8	1053	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S1PI370K4-625AXSP16	-	114.9	88.4	98.9	188.2	-	113.8	87.9	98.1	184.9	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI370K4-525AXSP16	68.10	106.7	81.5	91.7	177.4	68.3	105.8	81.1	91	174.5	145	25.4	2"	116	19.2	1-1/2"	174	35.7	2"
EAW-VD15S1PI370K4-425AXSP12	-	95.2	-	81.2	162.4	-	95	-	81	160.5	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI550K4-625AXSP16	-	129.6	99.4	111.5	213.2	-	128.5	99.1	110.7	210	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI550K4-525AXSP12	-	116.3	-	99.3	196.8	-	115.9	-	99.2	194.4	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI550K4-425AXSP12	-	106.6	79.7	90.8	182.7	-	106.4	80.1	90.7	180.5	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI750K4-625AXSP12	-	136.4	-	116.9	228.6	-	136.1	-	116.8	225.8	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD15S1PI750K4-525AXSP12	-	126.1	94.8	107.6	214	-	125.8	95.3	107.6	211.8	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI750K4-425AXSP12	-	115.4	86.3	98.2	198.2	-	115.1	86.6	98.1	196	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI370K5-625AXSP16	-	114.9	88.4	98.9	188.2	-	113.8	87.9	98.1	184.9	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI370K5-525AXSP16	68.10	106.7	81.5	91.7	177.4	68.3	105.8	81.1	91	174.5	145	25.4	2"	116	19.2	1-1/2"	174	35.7	2"
EAW-VD15S1PI370K5-425AXSP12	-	95.2	-	81.2	162.4	-	95	-	81	160.5	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI550K5-625AXSP16	-	129.6	99.4	111.5	213.2	-	128.5	99.1	110.7	210	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI550K5-525AXSP12	-	116.3	-	99.3	196.8	-	115.9	-	99.2	194.4	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI550K5-425AXSP12	-	106.6	79.7	90.8	182.7	-	106.4	80.1	90.7	180.5	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI750K5-625AXSP12	-	136.4	-	116.9	228.6	-	136.1	-	116.8	225.8	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD15S1PI750K5-525AXSP12	-	126.1	94.8	107.6	214	-	125.8	95.3	107.6	211.8	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI750K5-425AXSP12	-	115.4	86.3	98.2	198.2	-	115.1	86.6	98.1	196	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI370C4-625AXSP16	-	120	92.2	103.4	196.9	-	118.8	91.8	102.5	193.7	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI370C4-525AXSP12	-	107.9	-	92.3	182.2	-	107.5	-	92	179.7	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI370C4-425AXSP12	-	99	74.2	84.3	169.1	-	98.6	74.4	84.1	167.1	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI550C4-625AXSP12	-	132.6	-	113.5	221.7	-	132	-	113.2	218.7	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD15S1PI550C4-525AXSP12	-	121.9	91.8	104	206.8	-	121.5	92.2	103.9	204.4	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI550C4-425AXSP12	-	111.2	83.2	94.6	191.1	-	111	83.5	94.6	188.7	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI750C4-625AXSP12	-	141.9	-	121.3	238	-	141.6	-	121.4	235.3	242	18.6	3"	194	15.3	2"	291	26.1	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S1PI750C4-525AXSP12	-	130.7	98.2	111.5	222.3	-	130.4	98.6	111.5	219.8	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI750C4-425AXSP12	-	119.2	89.2	101.4	205.2	73.8	119.2	89.6	101.5	203	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI370C5-625AXSP16	-	120	92.2	103.4	196.9	-	118.8	91.8	102.5	193.7	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI370C5-525AXSP12	-	107.9	-	92.3	182.2	-	107.5	-	92	179.7	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI370C5-425AXSP12	-	99	74.2	84.3	169.1	-	98.6	74.4	84.1	167.1	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI550C5-625AXSP12	-	132.6	-	113.5	221.7	-	132	-	113.2	218.7	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD15S1PI550C5-525AXSP12	-	121.9	91.8	104	206.8	-	121.5	92.2	103.9	204.4	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI550C5-425AXSP12	-	111.2	83.2	94.6	191.1	-	111	83.5	94.6	188.7	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI750C5-625AXSP12	-	141.9	-	121.3	238	-	141.6	-	121.4	235.3	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD15S1PI750C5-525AXSP12	-	130.7	98.2	111.5	222.3	-	130.4	98.6	111.5	219.8	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI750C5-425AXSP12	-	119.2	89.2	101.4	205.2	73.8	119.2	89.6	101.5	203	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI370K8-625AXSP16	-	114.9	88.4	98.9	188.2	-	113.8	87.9	98.1	184.9	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI370K8-525AXSP16	68.10	106.7	81.5	91.7	177.4	68.3	105.8	81.1	91	174.5	145	25.4	2"	116	19.2	1-1/2"	174	35.7	2"
EAW-VD15S1PI370K8-425AXSP12	-	95.2	-	81.2	162.4	-	95	-	81	160.5	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI550K8-625AXSP16	-	129.6	99.4	111.5	213.2	-	128.5	99.1	110.7	210	182	26.6	2"	145	17.6	2"	218	37.3	2"
EAW-VD15S1PI550K8-525AXSP12	-	116.3	-	99.3	196.8	-	115.9	-	99.2	194.4	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI550K8-425AXSP12	-	106.6	79.7	90.8	182.7	-	106.4	80.1	90.7	180.5	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S1PI750K8-625AXSP12	-	136.4	-	116.9	228.6	-	136.1	-	116.8	225.8	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD15S1PI750K8-525AXSP12	-	126.1	94.8	107.6	214	-	125.8	95.3	107.6	211.8	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD15S1PI750K8-425AXSP12	-	115.4	86.3	98.2	198.2	-	115.1	86.6	98.1	196	157	19.9	2"	126	16	1-1/2"	189	28	2"
EAW-VD15S2PI370K4-625AXSP08	-	228.9	176.1	197.3	375.5	-	226.8	175.2	195.7	369	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI370K4-525AXSP08	-	216.7	165.6	186.2	359.5	-	214.8	164.9	184.7	353.6	303	22.6	3"	242	14.9	3"	363	31.7	3"
EAW-VD15S2PI370K4-425AXSP06	-	189.2	-	161.3	323.4	-	188.8	-	161.2	319.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI550K4-625AXSP08	-	258.2	198.1	222.2	425.4	-	256.1	197.3	220.6	419	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI550K4-525AXSP06	-	235	-	200.6	397.2	-	234.3	-	200.4	392.6	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI550K4-425AXSP06	-	211.8	158.6	180.3	363.3	-	211.4	159.1	180.3	359	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI750K4-625AXSP08	179.90	280.3	214.6	240.9	462.6	180.7	278.2	214.2	239.6	456.3	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI750K4-525AXSP06	-	254.8	191.7	217.2	432.5	-	254.1	192.3	217.2	427.5	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI750K4-425AXSP06	-	229.2	171.2	195	394.7	-	229.1	172	195.3	390.4	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI370K5-625AXSP08	-	228.9	176.1	197.3	375.5	-	226.8	175.2	195.7	369	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI370K5-525AXSP08	-	216.7	165.6	186.2	359.5	-	214.8	164.9	184.7	353.6	303	22.6	3"	242	14.9	3"	363	31.7	3"
EAW-VD15S2PI370K5-425AXSP06	-	189.2	-	161.3	323.4	-	188.8	-	161.2	319.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI550K5-625AXSP08	-	258.2	198.1	222.2	425.4	-	256.1	197.3	220.6	419	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI550K5-525AXSP06	-	235	-	200.6	397.2	-	234.3	-	200.4	392.6	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI550K5-425AXSP06	-	211.8	158.6	180.3	363.3	-	211.4	159.1	180.3	359	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI750K5-625AXSP08	179.90	280.3	214.6	240.9	462.6	180.7	278.2	214.2	239.6	456.3	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI750K5-525AXSP06	-	254.8	191.7	217.2	432.5	-	254.1	192.3	217.2	427.5	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI750K5-425AXSP06	-	229.2	171.2	195	394.7	-	229.1	172	195.3	390.4	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI370C4-625AXSP08	-	239.4	183.7	206	392.9	-	237.1	182.8	204.2	386.5	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI370C4-525AXSP08	144.20	226	172.5	194	375.3	144.6	224.1	171.8	192.5	369.6	303	22.6	3"	242	14.9	3"	363	31.7	3"
EAW-VD15S2PI370C4-425AXSP06	-	196.7	147.3	167.5	336.9	-	196.3	148	167.5	332.3	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI550C4-625AXSP08	175.00	271.9	208.3	233.8	448.5	175.4	269.6	207.5	232.1	442	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI550C4-525AXSP06	-	246.2	185.4	210.3	417.9	-	245.5	186	210	412.5	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI550C4-425AXSP06	-	221	165.5	188.3	380	-	220.5	165.9	188.2	375.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI750C4-625AXSP06	-	282.3	-	241.7	474.3	-	281.7	-	241.5	468.3	484	20	3"	388	13.2	3"	581	23.9	4"
EAW-VD15S2PI750C4-525AXSP06	-	264	198.7	225.2	448.8	-	263.4	199.4	225.3	443.7	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI750C4-425AXSP06	-	236.9	177	201.7	408.7	146.5	236.8	177.9	201.7	404.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI370C5-625AXSP08	-	239.4	183.7	206	392.9	-	237.1	182.8	204.2	386.5	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI370C5-525AXSP08	144.20	226	172.5	194	375.3	144.6	224.1	171.8	192.5	369.6	303	22.6	3"	242	14.9	3"	363	31.7	3"
EAW-VD15S2PI370C5-425AXSP06	-	196.7	147.3	167.5	336.9	-	196.3	148	167.5	332.3	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI550C5-625AXSP08	175.00	271.9	208.3	233.8	448.5	175.4	269.6	207.5	232.1	442	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI550C5-525AXSP06	-	246.2	185.4	210.3	417.9	-	245.5	186	210	412.5	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI550C5-425AXSP06	-	221	165.5	188.3	380	-	220.5	165.9	188.2	375.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI750C5-625AXSP06	-	282.3	-	241.7	474.3	-	281.7	-	241.5	468.3	484	20	3"	388	13.2	3"	581	23.9	4"
EAW-VD15S2PI750C5-525AXSP06	-	264	198.7	225.2	448.8	-	263.4	199.4	225.3	443.7	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI750C5-425AXSP06	-	236.9	177	201.7	408.7	146.5	236.8	177.9	201.7	404.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI370K8-625AXSP08	-	228.9	176.1	197.3	375.5	-	226.8	175.2	195.7	369	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI370K8-525AXSP08	-	216.7	165.6	186.2	359.5	-	214.8	164.9	184.7	353.6	303	22.6	3"	242	14.9	3"	363	31.7	3"
EAW-VD15S2PI370K8-425AXSP06	-	189.2	-	161.3	323.4	-	188.8	-	161.2	319.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI550K8-625AXSP08	-	258.2	198.1	222.2	425.4	-	256.1	197.3	220.6	419	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI550K8-525AXSP06	-	235	-	200.6	397.2	-	234.3	-	200.4	392.6	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI550K8-425AXSP06	-	211.8	158.6	180.3	363.3	-	211.4	159.1	180.3	359	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S2PI750K8-625AXSP08	179.90	280.3	214.6	240.9	462.6	180.7	278.2	214.2	239.6	456.3	363	23.3	3"	291	15.4	3"	436	32.8	3"
EAW-VD15S2PI750K8-525AXSP06	-	254.8	191.7	217.2	432.5	-	254.1	192.3	217.2	427.5	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD15S2PI750K8-425AXSP06	-	229.2	171.2	195	394.7	-	229.1	172	195.3	390.4	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD15S3PI370K4-625AXSP06	225.60	345.9	266.9	298.3	564.5	225.6	342.2	264.8	295.3	554.7	484	26.9	3"	388	17.7	3"	581	33.6	4"
EAW-VD15S3PI370K4-525AXSP04	-	313.2	-	-	528.3	-	312.3	-	-	521	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI370K4-425AXSP04	-	286	-	243.9	488.5	-	285.3	-	243.8	482.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI550K4-625AXSP04	-	373.9	-	-	625.8	-	372.5	-	-	617.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI550K4-525AXSP04	-	351.9	-	300.5	595.7	-	351	-	300.5	588.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI550K4-425AXSP04	-	320.2	239.6	272.8	549.6	-	319.5	240.7	272.7	543	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI750K4-625AXSP04	-	405.6	-	346.9	681	-	404.8	-	347.2	672.7	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI750K4-525AXSP04	-	381.7	287.2	325.8	648.8	-	381.2	288.5	325.8	641.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI750K4-425AXSP04	-	346.6	259.2	295.1	596.3	-	346.4	260.4	295.4	589.8	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI370K5-625AXSP06	225.60	345.9	266.9	298.3	564.5	225.6	342.2	264.8	295.3	554.7	484	26.9	3"	388	17.7	3"	581	33.6	4"
EAW-VD15S3PI370K5-525AXSP04	-	313.2	-	-	528.3	-	312.3	-	-	521	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI370K5-425AXSP04	-	286	-	243.9	488.5	-	285.3	-	243.8	482.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI550K5-625AXSP04	-	373.9	-	-	625.8	-	372.5	-	-	617.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI550K5-525AXSP04	-	351.9	-	300.5	595.7	-	351	-	300.5	588.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI550K5-425AXSP04	-	320.2	239.6	272.8	549.6	-	319.5	240.7	272.7	543	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI750K5-625AXSP04	-	405.6	-	346.9	681	-	404.8	-	347.2	672.7	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI750K5-525AXSP04	-	381.7	287.2	325.8	648.8	-	381.2	288.5	325.8	641.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI750K5-425AXSP04	-	346.6	259.2	295.1	596.3	-	346.4	260.4	295.4	589.8	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI370C4-625AXSP06	235.30	361.2	278.5	311.7	590.7	235.4	357.4	276.7	308.7	581.1	484	26.9	3"	388	17.7	3"	581	33.6	4"
EAW-VD15S3PI370C4-525AXSP04	-	326.5	-	-	551.4	-	325.2	-	-	543.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI370C4-425AXSP04	-	297.4	-	253.4	508.8	-	296.7	-	253.2	502.6	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI550C4-625AXSP04	-	393.6	-	336.8	660.4	-	392.5	-	336.3	651	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI550C4-525AXSP04	-	369.3	-	315.4	626.8	-	368.2	-	315	618.7	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI550C4-425AXSP04	-	334.3	250	284.4	574.9	-	333.4	251.1	284.7	567.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI750C4-625AXSP04	-	421.2	-	360.5	708.1	-	420.4	-	360.2	700	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI750C4-525AXSP04	-	396.1	297.5	337.8	673.1	-	395.1	299.1	338	665.5	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI750C4-425AXSP04	-	358.9	268	305.3	617.5	-	358.1	269.2	305.1	610.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI370C5-625AXSP06	235.30	361.2	278.5	311.7	590.7	235.4	357.4	276.7	308.7	581.1	484	26.9	3"	388	17.7	3"	581	33.6	4"
EAW-VD15S3PI370C5-525AXSP04	-	326.5	-	-	551.4	-	325.2	-	-	543.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI370C5-425AXSP04	-	297.4	-	253.4	508.8	-	296.7	-	253.2	502.6	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI550C5-625AXSP04	-	393.6	-	336.8	660.4	-	392.5	-	336.3	651	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI550C5-525AXSP04	-	369.3	-	315.4	626.8	-	368.2	-	315	618.7	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI550C5-425AXSP04	-	334.3	250	284.4	574.9	-	333.4	251.1	284.7	567.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI750C5-625AXSP04	-	421.2	-	360.5	708.1	-	420.4	-	360.2	700	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI750C5-525AXSP04	-	396.1	297.5	337.8	673.1	-	395.1	299.1	338	665.5	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI750C5-425AXSP04	-	358.9	268	305.3	617.5	-	358.1	269.2	305.1	610.7	484	19.4	3"	388	12.7	3"	581	23.1	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD15S3PI370K8-625AXSP06	225.60	345.9	266.9	298.3	564.5	225.6	342.2	264.8	295.3	554.7	484	26.9	3"	388	17.7	3"	581	33.6	4"
EAW-VD15S3PI370K8-525AXSP04	-	313.2	-	-	528.3	-	312.3	-	-	521	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI370K8-425AXSP04	-	286	-	243.9	488.5	-	285.3	-	243.8	482.7	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI550K8-625AXSP04	-	373.9	-	-	625.8	-	372.5	-	-	617.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI550K8-525AXSP04	-	351.9	-	300.5	595.7	-	351	-	300.5	588.9	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI550K8-425AXSP04	-	320.2	239.6	272.8	549.6	-	319.5	240.7	272.7	543	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S3PI750K8-625AXSP04	-	405.6	-	346.9	681	-	404.8	-	347.2	672.7	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD15S3PI750K8-525AXSP04	-	381.7	287.2	325.8	648.8	-	381.2	288.5	325.8	641.2	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD15S3PI750K8-425AXSP04	-	346.6	259.2	295.1	596.3	-	346.4	260.4	295.4	589.8	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD15S4PI370K4-625AXSP04	-	455.1	349.5	391.7	746.8	-	450.9	348.1	388.9	734.8	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI370K4-525AXSP04	-	430.1	328.4	369.2	714.7	-	426.9	327.1	366.9	703.9	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI370K4-425AXSP04	247.80	393.5	298	336.8	661.9	248.8	390.6	297.5	334.8	652.2	484	24	3"	388	15.8	3"	581	29.5	4"
EAW-VD15S4PI550K4-625AXSP04	-	513.2	393.5	441.5	846	-	509.1	392.1	438.4	833.3	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI550K4-525AXSP04	307.10	483.7	368.5	415	807.3	308.5	480.1	367.1	412.4	794.9	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI550K4-425AXSP02	-	-	-	-	697.8	-	-	-	-	692.9	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI750K4-625AXSP04	356.80	556.4	425.6	478.6	920.9	358.9	552.9	424.9	476.1	908.4	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI750K4-525AXSP02	-	-	-	-	826.1	-	-	-	-	820.2	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI750K4-425AXSP02	-	-	-	-	757	-	-	-	-	752.7	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI370K5-625AXSP04	-	455.1	349.5	391.7	746.8	-	450.9	348.1	388.9	734.8	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI370K5-525AXSP04	-	430.1	328.4	369.2	714.7	-	426.9	327.1	366.9	703.9	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI370K5-425AXSP04	247.80	393.5	298	336.8	661.9	248.8	390.6	297.5	334.8	652.2	484	24	3"	388	15.8	3"	581	29.5	4"
EAW-VD15S4PI550K5-625AXSP04	-	513.2	393.5	441.5	846	-	509.1	392.1	438.4	833.3	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI550K5-525AXSP04	307.10	483.7	368.5	415	807.3	308.5	480.1	367.1	412.4	794.9	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI550K5-425AXSP02	-	-	-	-	697.8	-	-	-	-	692.9	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI750K5-625AXSP04	356.80	556.4	425.6	478.6	920.9	358.9	552.9	424.9	476.1	908.4	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI750K5-525AXSP02	-	-	-	-	826.1	-	-	-	-	820.2	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI750K5-425AXSP02	-	-	-	-	757	-	-	-	-	752.7	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI370C4-625AXSP04	-	475.3	365	409.3	781.4	-	471.4	363.2	405.9	768.8	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI370C4-525AXSP04	285.70	448.5	342	384.8	746	287	444.6	340.7	382.4	734.8	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI370C4-425AXSP02	-	-	-	-	646.7	-	-	-	-	641.2	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI550C4-625AXSP04	347.00	540.5	413.8	464.6	893	348.3	536	412.2	461.2	879	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI550C4-525AXSP02	-	-	-	-	798.5	-	-	-	-	791.8	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI550C4-425AXSP02	-	-	-	-	729.3	-	-	-	-	723.8	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI750C4-625AXSP04	370.60	578.7	442.3	496.9	958.8	372.2	575	441.4	494.2	945.5	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI750C4-525AXSP02	-	-	-	-	856.6	-	-	-	-	852.1	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI750C4-425AXSP02	-	-	-	-	783.4	-	-	-	-	779	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI370C5-625AXSP04	-	475.3	365	409.3	781.4	-	471.4	363.2	405.9	768.8	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI370C5-525AXSP04	285.70	448.5	342	384.8	746	287	444.6	340.7	382.4	734.8	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI370C5-425AXSP02	-	-	-	-	646.7	-	-	-	-	641.2	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI550C5-625AXSP04	347.00	540.5	413.8	464.6	893	348.3	536	412.2	461.2	879	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI550C5-525AXSP02	-	-	-	-	798.5	-	-	-	-	791.8	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI550C5-425AXSP02	-	-	-	-	729.3	-	-	-	-	723.8	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI750C5-625AXSP04	370.60	578.7	442.3	496.9	958.8	372.2	575	441.4	494.2	945.5	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI750C5-525AXSP02	-	-	-	-	856.6	-	-	-	-	852.1	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI750C5-425AXSP02	-	-	-	-	783.4	-	-	-	-	779	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI370K8-625AXSP04	-	455.1	349.5	391.7	746.8	-	450.9	348.1	388.9	734.8	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI370K8-525AXSP04	-	430.1	328.4	369.2	714.7	-	426.9	327.1	366.9	703.9	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI370K8-425AXSP04	247.80	393.5	298	336.8	661.9	248.8	390.6	297.5	334.8	652.2	484	24	3"	388	15.8	3"	581	29.5	4"
EAW-VD15S4PI550K8-625AXSP04	-	513.2	393.5	441.5	846	-	509.1	392.1	438.4	833.3	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI550K8-525AXSP04	307.10	483.7	368.5	415	807.3	308.5	480.1	367.1	412.4	794.9	606	21.8	4"	484	17.4	3"	727	30.6	4"
EAW-VD15S4PI550K8-425AXSP02	-	-	-	-	697.8	-	-	-	-	692.9	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S4PI750K8-625AXSP04	356.80	556.4	425.6	478.6	920.9	358.9	552.9	424.9	476.1	908.4	727	22.8	4"	581	15	4"	872	32.1	4"
EAW-VD15S4PI750K8-525AXSP02	-	-	-	-	826.1	-	-	-	-	820.2	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD15S4PI750K8-425AXSP02	-	-	-	-	757	-	-	-	-	752.7	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD15S5PI370K4-625AXSP02	-	-	-	-	901.2	-	-	-	-	890	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI370K4-525AXSP02	-	-	-	-	859	-	-	-	-	848.5	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI370K4-425AXSP02	-	456.3	-	-	792	-	457.1	-	-	784.1	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI550K4-625AXSP02	-	-	-	-	1018.8	-	-	-	-	1007.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI550K4-525AXSP02	-	562.7	-	-	967.9	-	564.1	-	-	958.4	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI550K4-425AXSP02	-	510	-	-	889	-	511.9	-	-	881.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI750K4-625AXSP02	-	-	-	-	1108.2	-	-	-	-	1097.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI750K4-525AXSP02	-	609.6	-	-	1052.1	-	612	-	-	1042.9	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI750K4-425AXSP02	-	552.1	-	467.6	965	-	554.2	-	470.5	956.3	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI370K5-625AXSP02	-	-	-	-	901.2	-	-	-	-	890	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI370K5-525AXSP02	-	-	-	-	859	-	-	-	-	848.5	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI370K5-425AXSP02	-	456.3	-	-	792	-	457.1	-	-	784.1	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI550K5-625AXSP02	-	-	-	-	1018.8	-	-	-	-	1007.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI550K5-525AXSP02	-	562.7	-	-	967.9	-	564.1	-	-	958.4	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI550K5-425AXSP02	-	510	-	-	889	-	511.9	-	-	881.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI750K5-625AXSP02	-	-	-	-	1108.2	-	-	-	-	1097.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI750K5-525AXSP02	-	609.6	-	-	1052.1	-	612	-	-	1042.9	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI750K5-425AXSP02	-	552.1	-	467.6	965	-	554.2	-	470.5	956.3	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI370C4-625AXSP02	-	-	-	-	942.6	-	-	-	-	930.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI370C4-525AXSP02	-	-	-	-	896.4	-	-	-	-	886.6	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI370C4-425AXSP02	-	474.2	-	-	824.7	-	475.1	-	-	816.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI550C4-625AXSP02	-	-	-	-	1074.8	-	-	-	-	1062.3	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI550C4-525AXSP02	-	590	-	-	1016.8	-	591.5	-	-	1006.6	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI550C4-425AXSP02	-	532.8	-	450.9	929.4	-	533.8	-	453.6	920.8	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI750C4-625AXSP02	-	674.2	-	-	1151.9	-	676.1	-	-	1141.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI750C4-525AXSP02	-	632.2	-	-	1092.7	-	634.2	-	-	1082.1	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI750C4-425AXSP02	-	571.3	-	483.4	999	-	573.6	-	486.5	991.4	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI370C5-625AXSP02	-	-	-	-	942.6	-	-	-	-	930.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI370C5-525AXSP02	-	-	-	-	896.4	-	-	-	-	886.6	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI370C5-425AXSP02	-	474.2	-	-	824.7	-	475.1	-	-	816.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI550C5-625AXSP02	-	-	-	-	1074.8	-	-	-	-	1062.3	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI550C5-525AXSP02	-	590	-	-	1016.8	-	591.5	-	-	1006.6	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI550C5-425AXSP02	-	532.8	-	450.9	929.4	-	533.8	-	453.6	920.8	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI750C5-625AXSP02	-	674.2	-	-	1151.9	-	676.1	-	-	1141.9	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI750C5-525AXSP02	-	632.2	-	-	1092.7	-	634.2	-	-	1082.1	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI750C5-425AXSP02	-	571.3	-	483.4	999	-	573.6	-	486.5	991.4	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI370K8-625AXSP02	-	-	-	-	901.2	-	-	-	-	890	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI370K8-525AXSP02	-	-	-	-	859	-	-	-	-	848.5	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI370K8-425AXSP02	-	456.3	-	-	792	-	457.1	-	-	784.1	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI550K8-625AXSP02	-	-	-	-	1018.8	-	-	-	-	1007.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI550K8-525AXSP02	-	562.7	-	-	967.9	-	564.1	-	-	958.4	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI550K8-425AXSP02	-	510	-	-	889	-	511.9	-	-	881.2	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD15S5PI750K8-625AXSP02	-	-	-	-	1108.2	-	-	-	-	1097.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD15S5PI750K8-525AXSP02	-	609.6	-	-	1052.1	-	612	-	-	1042.9	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD15S5PI750K8-425AXSP02	-	552.1	-	467.6	965	-	554.2	-	470.5	956.3	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD9102ZA320P7-625AXSP16	-	-	-	-	170.7	-	-	-	-	169.2	242	15.3	3"	194	13.3	2"	291	21.5	3"
EAW-VD9102ZA320P7-525AXSP16	-	-	-	-	157.8	-	90.3	-	-	156.7	194	18.1	2"	155	11.9	2"	232	25.4	2"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9102ZA320P7-425AXSP16	-	81.1	-	-	144.7	-	81.9	-	-	143.7	157	16.7	2"	126	14.1	1-1/2"	189	23.5	2"
EAW-VD9104ZA320P7-625AXSP12	-	209.6	158.5	179.2	352.9	-	208.9	159	179.1	348.9	327	19.6	3"	262	12.9	3"	392	27.5	3"
EAW-VD9104ZA320P7-525AXSP12	-	193.9	145.6	165.2	330.6	-	193.4	146.2	165.2	326.8	266	18.9	3"	213	16.3	2"	320	26.5	3"
EAW-VD9104ZA320P7-425AXSP12	107.60	177	132.1	150.3	304.9	109.2	176.7	132.7	150.6	301.6	218	22.4	2"	174	14.8	2"	262	25.9	3"
EAW-VD9106ZA320P7-625AXSP08	-	311.9	235.6	266.5	525.5	-	310.9	236.5	266.4	519.5	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD9106ZA320P7-525AXSP08	-	289.9	217.6	247	494.5	-	289.3	218.5	247	488.9	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD9106ZA320P7-425AXSP08	160.80	264.6	197.3	225.1	456	163.2	264.1	198.4	225.1	451.7	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD9108ZA320P7-625AXSP06	-	417	315	356.3	702.4	-	416.2	316.2	356.2	694.4	654	18.3	4"	523	12.1	4"	785	25.7	4"
EAW-VD9108ZA320P7-525AXSP06	-	390	292.6	332.6	664.7	-	389.2	294.3	332.4	657.1	545	17.5	4"	436	14.1	3"	654	24.6	4"
EAW-VD9108ZA320P7-425AXSP06	213.60	351.7	262.6	299	607.1	216.7	351	263.5	299	600.5	436	19.3	3"	349	12.7	3"	523	23.6	4"
EAW-VD9110ZA320P7-625AXSP04	-	505.7	-	-	864.1	-	507.2	-	-	855.5	981	14.2	(2) 4"	785	12.3	4"	1177	20	(2) 4"
EAW-VD9110ZA320P7-525AXSP04	-	470.8	-	399.8	813.2	-	471.6	-	401.9	806.3	812	16.8	4"	649	11.1	4"	974	19.3	(2) 4"
EAW-VD9110ZA320P7-425AXSP04	-	425.3	314.2	360	744	-	427	317.6	362.4	737.2	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD9112ZA320P7-625AXSP04	-	622.1	469.7	531.4	1049.8	-	621	471.5	532	1037.8	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD9112ZA320P7-525AXSP04	-	578.9	434.5	493.3	989.1	-	578.6	436.4	493.9	977.9	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD9112ZA320P7-425AXSP04	317.70	523.9	390.9	445.2	905.2	323.1	523.9	393	446.1	895.4	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD9114ZA320P7-625AXSP04	465.90	738.6	561.3	632.6	1235.3	470	735.1	561.4	630.3	1219.6	981	18.8	(2) 4"	785	15.3	4"	1177	26.4	(2) 4"
EAW-VD9114ZA320P7-525AXSP04	428.30	687.7	518.9	587.6	1164.8	432.6	685	520	586.2	1149.9	812	21.4	4"	649	14.1	4"	974	25.7	(2) 4"
EAW-VD9114ZA320P7-425AXSP02	-	-	-	-	987.2	-	-	-	-	983.8	1308	11.3	(2) 4"	1046	7.4	(2) 4"	1570	15.9	(2) 4"
EAW-VD9116ZA320P7-625AXSP02	-	-	-	-	1339.8	-	-	-	-	1330.3	1962	12.5	(3) 4"	1570	10.3	(2) 4"	2354	17.5	(3) 4"
EAW-VD9116ZA320P7-525AXSP02	-	-	-	-	1262.2	-	-	-	-	1253.8	1635	14	(2) 4"	1308	9.2	(2) 4"	1962	16.4	(3) 4"
EAW-VD9116ZA320P7-425AXSP02	-	639.4	-	-	1146.5	-	646.9	-	-	1140.4	1308	12.5	(2) 4"	1046	8.2	(2) 4"	1570	17.5	(2) 4"
EAW-VD9118ZA320P7-625AXSP02	-	-	-	-	1522.7	-	-	-	-	1509.8	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD9118ZA320P7-525AXSP02	-	819.9	-	-	1435.9	-	825.8	-	-	1424.1	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD9118ZA320P7-425AXSP02	-	737	-	620.9	1304.2	-	742.3	-	627.1	1295	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD9120ZA320P7-625AXSP02	-	994.6	-	-	1706.9	-	997.8	-	-	1690	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD9120ZA320P7-525AXSP02	-	927	-	786.3	1608.7	-	930.3	-	792.1	1593.2	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD9120ZA320P7-425AXSP02	-	833.9	614.4	705	1462.8	-	836.5	621.7	710.1	1450	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD9102ZJ320P7-625AXSP16	-	-	-	-	180.5	-	-	-	-	178.7	242	16.4	3"	194	14	2"	291	22.9	3"
EAW-VD9102ZJ320P7-525AXSP16	-	95.9	-	-	167	-	96.4	-	-	165.6	194	19.1	2"	155	12.6	2"	232	26.8	2"
EAW-VD9102ZJ320P7-425AXSP16	-	86.9	-	73.4	153.2	-	87.3	-	74	151.9	157	17.8	2"	126	14.8	1-1/2"	189	25	2"
EAW-VD9104ZJ320P7-625AXSP12	-	222.6	169.3	190.9	372	-	221.5	169.3	190.2	366.8	327	21.1	3"	262	14	3"	392	29.7	3"
EAW-VD9104ZJ320P7-525AXSP12	128.30	205.9	155.5	175.9	348.2	129.5	204.8	155.5	175.5	343.7	266	20.4	3"	213	17.3	2"	320	28.7	3"
EAW-VD9104ZJ320P7-425AXSP08	-	176.9	-	-	311.1	-	178	-	-	308.8	327	14.8	3"	262	9.7	3"	392	20.8	3"
EAW-VD9106ZJ320P7-625AXSP08	-	331.3	251.8	284	554.1	-	329.7	251.8	283	546.3	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD9106ZJ320P7-525AXSP08	191.70	308	232.5	263.1	521.5	193.6	306.8	232.6	262.4	514.2	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD9106ZJ320P7-425AXSP06	-	269.9	-	228.7	470.2	-	270.1	201.7	229.7	466	436	17	3"	349	11.2	3"	523	20.4	4"
EAW-VD9108ZJ320P7-625AXSP06	-	443.5	336.7	379.7	740.6	-	440.7	336.7	378.3	731	654	19.8	4"	523	13.1	4"	785	27.9	4"
EAW-VD9108ZJ320P7-525AXSP06	257.80	414.3	313	354	700.9	260.7	412.6	313.1	353.1	691.8	545	19	4"	436	15.1	3"	654	26.7	4"
EAW-VD9108ZJ320P7-425AXSP06	229.70	373.5	280.2	318.4	639.1	232.1	372.1	280.5	317.8	631.3	436	20.9	3"	349	13.7	3"	523	25.7	4"
EAW-VD9110ZJ320P7-625AXSP04	-	539.8	-	460.7	912.4	-	538.8	-	461.2	901.9	981	15.5	(2) 4"	785	13.1	4"	1177	21.7	(2) 4"
EAW-VD9110ZJ320P7-525AXSP04	-	502.1	375.5	427.5	859	-	501.1	377.8	428.1	849.2	812	18.1	4"	649	11.9	4"	974	21.1	(2) 4"
EAW-VD9110ZJ320P7-425AXSP04	-	453.7	337.3	385.3	786	-	453.9	339.9	385.6	777.8	654	16.7	4"	523	11	4"	785	23.4	4"
EAW-VD9112ZJ320P7-625AXSP04	-	661.8	502.1	566.4	1106.8	-	658.5	502.2	565.1	1092.6	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD9112ZJ320P7-525AXSP04	382.80	616	464.2	526.1	1043.1	386.6	612.7	465.2	524.9	1029.7	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD9112ZJ320P7-425AXSP04	341.90	556.5	418	474.2	954.5	346.2	554.6	418.5	473.4	942.9	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD9114ZJ320P7-625AXSP04	499.80	783.3	597.8	672.9	1302.2	502.3	778.2	596.8	668.4	1282.2	981	20.6	(2) 4"	785	16.5	4"	1177	28.9	(2) 4"
EAW-VD9114ZJ320P7-525AXSP02	-	-	-	-	1154.9	-	-	-	-	1145.5	1635	13.7	(2) 4"	1308	9	(2) 4"	1962	16	(3) 4"
EAW-VD9114ZJ320P7-425AXSP02	-	-	-	-	1048	-	-	-	-	1041.1	1308	12.2	(2) 4"	1046	8	(2) 4"	1570	17.2	(2) 4"
EAW-VD9116ZJ320P7-625AXSP02	-	-	-	-	1419.2	-	-	-	-	1405.1	1962	13.5	(3) 4"	1570	11	(2) 4"	2354	19	(3) 4"
EAW-VD9116ZJ320P7-525AXSP02	-	763.9	-	-	1336.2	-	768	-	-	1323.3	1635	15	(2) 4"	1308	9.8	(2) 4"	1962	17.8	(3) 4"
EAW-VD9116ZJ320P7-425AXSP02	-	686.5	-	-	1214.6	-	690.3	-	-	1204.4	1308	13.5	(2) 4"	1046	8.9	(2) 4"	1570	19	(2) 4"
EAW-VD9118ZJ320P7-625AXSP02	-	941.6	-	-	1610.5	-	943.1	-	-	1594.3	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD9118ZJ320P7-525AXSP02	-	876.9	-	-	1517.6	-	879.7	-	-	1502.7	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD9118ZJ320P7-425AXSP02	-	787.6	-	667.1	1379	-	790.1	-	670.7	1367.2	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD9102PA320P7-625AXSP16	-	-	-	-	146.3	-	84.6	-	-	145.6	182	17.4	2"	145	11.5	2"	218	24.5	2"
EAW-VD9102PA320P7-525AXSP16	-	76.7	-	-	135.9	-	77.7	-	-	135.4	145	16.2	2"	116	13.2	1-1/2"	174	22.8	2"
EAW-VD9102PA320P7-425AXSP16	-	71	-	59.7	127	-	71.8	-	60.6	126.6	121	18.2	1-1/2"	97	12	1-1/2"	145	21.9	2"
EAW-VD9104PA320P7-625AXSP12	-	177.9	134.2	152.1	301.3	112.1	178.1	135.1	152.5	299	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD9104PA320P7-525AXSP12	99.80	163.3	122.3	139	280.2	101.5	163.5	123.2	139.4	278.2	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD9104PA320P7-425AXSP08	-	141.1	-	118.7	252.8	-	142.9	-	120.6	252	242	12.8	3"	194	11.4	2"	291	17.9	3"
EAW-VD9106PA320P7-625AXSP08	-	266.2	200.7	227.5	450.9	-	266.4	202.1	228	447.4	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD9106PA320P7-525AXSP08	152.90	250.1	187.4	212.8	428.1	155.7	250.3	188.7	213.7	424.9	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD9106PA320P7-425AXSP06	-	212.5	155.5	179.2	376.7	-	214.3	158.3	181.2	375	315	14	3"	252	9.3	3"	378	19.7	3"
EAW-VD9108PA320P7-625AXSP06	-	353.9	266.8	302.4	600.4	-	354.3	268.6	303.1	595	484	20	3"	388	13.2	3"	581	23.9	4"
EAW-VD9108PA320P7-525AXSP06	202.00	330.3	247.2	281.4	566.9	205.7	330.6	249.1	282.1	562.6	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD9108PA320P7-425AXSP04	-	279.5	-	234.7	500.5	-	282.5	-	238.4	499.1	484	14.8	3"	388	9.7	3"	581	16.6	4"
EAW-VD9110PA320P7-625AXSP04	-	429.2	-	364.8	737.2	-	431.8	-	367.8	732.6	727	15.9	4"	581	10.5	4"	872	22.4	4"
EAW-VD9110PA320P7-525AXSP04	-	402.4	298.5	341	699.6	-	404.3	302.1	343.9	694.5	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD9110PA320P7-425AXSP04	-	363.8	267.9	307.5	639.3	-	365.9	271.7	310.1	635.2	484	17.1	3"	388	11.2	3"	581	19.8	4"
EAW-VD9112PA320P7-625AXSP04	-	527.8	397.6	450.8	896	-	529.2	400.4	452	889.2	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD9112PA320P7-525AXSP04	302.40	495.5	370.8	421.4	850.3	308	496	373.6	423.2	844	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD9112PA320P7-425AXSP02	-	-	-	-	711.8	-	-	-	-	713.2	969	8.9	(2) 4"	775	8.6	4"	1163	12.5	(2) 4"
EAW-VD9114PA320P7-625AXSP04	393.30	627.2	475	536.3	1054.7	398.1	625.9	476.5	536.8	1045.2	727	20.5	4"	581	13.5	4"	872	28.8	4"
EAW-VD9114PA320P7-525AXSP02	-	-	-	-	930.6	-	-	-	-	928.8	1211	10.8	(2) 4"	969	7.1	(2) 4"	1453	15.3	(2) 4"
EAW-VD9114PA320P7-425AXSP02	-	462.8	-	-	846.6	-	471.8	-	-	846.3	969	10	(2) 4"	775	9.4	4"	1163	14.1	(2) 4"
EAW-VD9116PA320P7-625AXSP02	-	-	-	-	1141.5	-	-	-	-	1138	1453	13	(2) 4"	1163	8.5	(2) 4"	1744	18.3	(2) 4"
EAW-VD9116PA320P7-525AXSP02	-	606.1	-	-	1079.5	-	614.1	-	-	1075.5	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD9116PA320P7-425AXSP02	-	546	-	458.3	982.6	-	553.2	-	466	980.3	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD9118PA320P7-625AXSP02	-	745.5	-	-	1297.9	-	752.9	-	-	1291.9	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD9118PA320P7-525AXSP02	-	697.2	-	589	1227	-	704.7	-	596.9	1222.2	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD9118PA320P7-425AXSP02	-	628.8	459.2	529.7	1118.7	-	634.4	468.2	536.4	1113.9	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD9120PA320P7-625AXSP02	-	843.4	-	717.1	1455.4	-	848.9	-	723.2	1446.7	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD9120PA320P7-525AXSP02	-	789.1	583.8	668.8	1375.3	-	794.6	592.4	674.9	1367.7	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD9120PA320P7-425AXSP02	-	711.1	523.5	601.1	1255.5	-	717	531	607.1	1247.9	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD9102PJ320P7-625AXSP16	-	90.8	-	-	156.8	-	91.3	-	-	155.6	182	18.4	2"	145	12.1	2"	218	25.9	2"
EAW-VD9102PJ320P7-525AXSP16	-	83.1	-	70.3	145.4	-	83.8	-	71	144.6	145	17.3	2"	116	13.8	1-1/2"	174	24.2	2"
EAW-VD9102PJ320P7-425AXSP16	-	76.8	56.3	64.8	135.7	-	77.4	57.2	65.4	135	121	19.3	1-1/2"	97	12.7	1-1/2"	145	23.3	2"
EAW-VD9104PJ320P7-625AXSP12	120.20	191.6	145	163.8	321.5	121.6	191.2	145.4	163.7	318.2	242	20.2	3"	194	16.3	2"	291	28.3	3"
EAW-VD9104PJ320P7-525AXSP08	-	169.1	-	143.1	295.8	-	170.5	-	144.6	294	303	14.4	3"	242	9.5	3"	363	20.2	3"
EAW-VD9104PJ320P7-425AXSP08	-	152.8	-	129	270.1	-	153.9	113.9	130.4	268.8	242	13.8	3"	194	12.1	2"	291	19.3	3"
EAW-VD9106PJ320P7-625AXSP08	179.70	286.6	217.1	245	481.7	181.8	286	217.8	245.2	476.7	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD9106PJ320P7-525AXSP06	-	256.5	190.5	217.7	444.9	-	257.7	192.7	219.1	441.7	400	16.3	3"	320	10.7	3"	480	22.9	3"
EAW-VD9106PJ320P7-425AXSP06	-	229.1	169.2	194	402.5	-	230.5	171.3	195.6	400	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD9108PJ320P7-625AXSP06	238.80	381.1	288.6	325.7	640.7	241.7	380.3	289.6	325.9	634	484	21.5	3"	388	14.2	3"	581	26.1	4"
EAW-VD9108PJ320P7-525AXSP04	-	334.9	-	283.3	587.4	-	337.7	-	286.4	584	606	13.7	4"	484	11.9	3"	727	19.2	4"
EAW-VD9108PJ320P7-425AXSP04	-	302.1	-	255.1	535.9	-	304.6	225.1	257.7	532.5	484	15.8	3"	388	10.4	3"	581	18	4"
EAW-VD9110PJ320P7-625AXSP04	-	463.2	347.5	395.2	788.9	-	464.4	350.6	396.3	781.8	727	17.2	4"	581	11.3	4"	872	24.2	4"
EAW-VD9110PJ320P7-525AXSP04	-	433.7	323.8	369	746.7	-	434.9	326.9	370.7	741.2	606	16.2	4"	484	13.6	3"	727	22.8	4"
EAW-VD9110PJ320P7-425AXSP04	234.60	391.9	290.4	332.3	681.8	239.7	392.5	293.2	333.6	677.3	484	18.4	3"	388	12.1	3"	581	21.6	4"
EAW-VD9112PJ320P7-625AXSP04	355.30	568.5	430.3	486.4	957.4	360.3	567.3	431.7	486.1	947.5	727	19.7	4"	581	13	4"	872	27.8	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9112PJ320P7-525AXSP02	-	-	-	-	840	-	-	-	-	839.5	1211	10.5	(2) 4"	969	6.9	(2) 4"	1453	14.7	(2) 4"
EAW-VD9112PJ320P7-425AXSP02	-	-	-	-	764.7	-	-	-	-	764.5	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD9114PJ320P7-625AXSP02	-	-	-	-	1057.1	-	-	-	-	1053.7	1453	12.7	(2) 4"	1163	8.4	(2) 4"	1744	17.9	(2) 4"
EAW-VD9114PJ320P7-525AXSP02	-	-	-	-	997.4	-	567.7	-	-	995.1	1211	11.7	(2) 4"	969	7.7	(2) 4"	1453	16.5	(2) 4"
EAW-VD9114PJ320P7-425AXSP02	-	503.6	-	-	908.9	-	510.5	-	-	905.2	969	10.9	(2) 4"	775	10	4"	1163	15.4	(2) 4"
EAW-VD9116PJ320P7-625AXSP02	-	703.4	-	-	1224	-	709.2	-	-	1216.7	1453	14	(2) 4"	1163	9.2	(2) 4"	1744	19.7	(2) 4"
EAW-VD9116PJ320P7-525AXSP02	-	656.8	-	-	1156.5	-	662.7	-	562	1148.6	1211	13	(2) 4"	969	8.6	(2) 4"	1453	18.3	(2) 4"
EAW-VD9116PJ320P7-425AXSP02	-	591.6	-	498.2	1052.6	-	596.9	-	504.5	1046.4	969	12.2	(2) 4"	775	10.8	4"	1163	17.2	(2) 4"
EAW-VD9118PJ320P7-625AXSP02	-	807.9	-	686.6	1389.6	-	811.7	-	691.3	1379.3	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD9118PJ320P7-525AXSP02	-	754.9	-	639.6	1314.2	-	758.7	566.1	644.3	1304.9	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD9118PJ320P7-425AXSP02	-	679.7	500	574.5	1195.9	-	684	507.1	578.7	1188.6	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD91S1MA320P7-625AXSP16	-	-	-	-	83.9	-	-	-	-	83.4	109	18.1	1-1/2"	87	11.9	1-1/2"	131	25.5	1-1/2"
EAW-VD91S1MA320P7-525AXSP16	-	44.8	-	-	79	-	45.3	-	-	78.5	97	16.6	1-1/2"	78	10.9	1-1/2"	116	23.3	1-1/2"
EAW-VD91S1MA320P7-425AXSP16	-	40.8	-	34.4	72.3	-	41.1	-	34.8	71.8	73	16.4	1-1/2"	58	10.8	1-1/2"	87	23	1-1/2"
EAW-VD91S2MA320P7-625AXSP12	-	102.8	77.6	88	173.4	-	102.6	78	87.9	171.2	157	19.8	2"	126	15.7	1-1/2"	189	27.8	2"
EAW-VD91S2MA320P7-525AXSP12	60.30	97.2	73.3	83	165	61	97	73.5	82.9	163	121	22.7	1-1/2"	97	15	1-1/2"	145	28.5	2"
EAW-VD91S2MA320P7-425AXSP08	-	81.2	-	-	144.5	-	81.9	-	-	143.7	157	13.9	2"	126	11.8	1-1/2"	189	19.6	2"
EAW-VD91S3MA320P7-625AXSP08	-	152.1	114.7	129.8	256.6	-	151.7	115.2	129.9	253.8	230	21.1	2"	184	13.9	2"	276	24.1	3"
EAW-VD91S3MA320P7-525AXSP08	-	142.7	107.3	121.8	243.6	-	142.7	107.8	121.8	240.9	194	19.7	2"	155	13	2"	232	27.7	2"
EAW-VD91S3MA320P7-425AXSP08	78.90	129.8	97	110.5	224.3	80.1	129.8	97.4	110.6	221.9	157	18.5	2"	126	14.8	1-1/2"	189	26	2"
EAW-VD91S4MA320P7-625AXSP06	-	204.7	154.6	174.9	345.1	-	204.2	155.2	174.9	341.3	315	17.4	3"	252	11.5	3"	378	24.4	3"
EAW-VD91S4MA320P7-525AXSP06	-	188.3	141.3	160.5	321.7	-	188	141.8	160.6	318.2	254	16.8	3"	204	14.1	2"	305	23.5	3"
EAW-VD91S4MA320P7-425AXSP06	103.50	170.7	127.4	144.9	294.9	105.1	170.5	127.9	145.3	291.9	206	19.5	2"	165	12.8	2"	247	23	3"
EAW-VD91S5MA320P7-625AXSP04	-	248.3	-	-	424.5	-	248.8	-	-	420.4	472	16.7	3"	378	11	3"	567	19.7	4"
EAW-VD91S5MA320P7-525AXSP04	-	229.9	-	195.1	398.3	-	230.8	-	196.2	394.6	388	15.4	3"	310	10.1	3"	465	21.6	3"
EAW-VD91S5MA320P7-425AXSP04	-	208.9	154.2	176.7	365.8	-	209.5	155.9	178	362.6	315	14.5	3"	252	9.5	3"	378	20.3	3"
EAW-VD91S6MA320P7-625AXSP04	-	305.4	230.5	260.8	515.7	-	305	231.5	260.9	510	472	19	3"	378	12.5	3"	567	22.9	4"
EAW-VD91S6MA320P7-525AXSP04	-	283.3	212.3	241.2	483.9	-	282.9	213.4	241.6	478.6	388	17.7	3"	310	11.7	3"	465	24.9	3"
EAW-VD91S6MA320P7-425AXSP04	155.90	257.3	191.8	218.6	444.4	158.5	257	193	219.1	440.5	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-VD9102ZA247I6-625AXSP16	-	-	-	-	150.1	-	-	-	-	148.9	242	15.3	3"	194	13.3	2"	291	21.5	3"
EAW-VD9102ZA247I6-525AXSP16	-	-	-	-	140.3	-	-	-	-	139.2	194	18.1	2"	155	11.9	2"	232	25.4	2"
EAW-VD9102ZA247I6-425AXSP16	-	73	-	-	129.6	-	73.7	-	-	128.9	157	16.7	2"	126	14.1	1-1/2"	189	23.5	2"
EAW-VD9104ZA247I6-625AXSP12	-	185	-	158.5	310.1	-	184.7	-	158.5	306.4	327	19.6	3"	262	12.9	3"	392	27.5	3"
EAW-VD9104ZA247I6-525AXSP12	-	172.6	129.8	147.3	293	-	172.2	130.5	147.4	289.7	266	18.9	3"	213	16.3	2"	320	26.5	3"
EAW-VD9104ZA247I6-425AXSP12	-	158.8	119	135.3	273	-	158.8	119.5	135.3	270	218	22.4	2"	174	14.8	2"	262	25.9	3"
EAW-VD9106ZA247I6-625AXSP08	-	275.4	-	235.8	462.4	-	275	-	235.8	456.9	484	20.8	3"	388	13.7	3"	581	24.9	4"
EAW-VD9106ZA247I6-525AXSP08	-	258.2	194.1	220.3	438.4	-	257.9	195.1	220.4	433.5	400	19.4	3"	320	12.8	3"	480	27.2	3"
EAW-VD9106ZA247I6-425AXSP08	-	237.5	177.8	202.3	408.3	-	237.4	178.6	202.5	403.9	327	18.3	3"	262	12.1	3"	392	25.8	3"
EAW-VD9108ZA247I6-625AXSP08	242.60	378.2	289.4	325	625.3	243.8	375.5	288.6	323.4	617	484	25.4	3"	388	16.7	3"	581	31.3	4"
EAW-VD9108ZA247I6-525AXSP06	-	347.2	261.3	296.4	589.1	-	346.8	262.6	296.6	582.4	545	17.5	4"	436	14.1	3"	654	24.6	4"
EAW-VD9108ZA247I6-425AXSP06	-	315.6	236.2	268.8	542.8	-	315.5	237.3	269.1	537	436	19.3	3"	349	12.7	3"	523	23.6	4"
EAW-VD9110ZA247I6-625AXSP06	-	471	360.2	404.6	781.6	303	468.8	359.7	403.1	771.3	654	21.8	4"	523	14.4	4"	785	30.6	4"
EAW-VD9110ZA247I6-525AXSP04	-	419.1	-	-	722.2	-	420.8	-	-	715.1	812	16.8	4"	649	11.1	4"	974	19.3	(2) 4"
EAW-VD9110ZA247I6-425AXSP04	-	382.3	-	324.2	666.7	-	383.7	-	326.1	660.8	654	15.4	4"	523	10.1	4"	785	21.6	4"
EAW-VD9112ZA247I6-625AXSP04	-	550.1	-	470.4	923.7	-	549.2	-	471	912.7	981	16.5	(2) 4"	785	13.8	4"	1177	23.2	(2) 4"
EAW-VD9112ZA247I6-525AXSP04	-	516.3	388.2	440.5	876.8	-	515.1	389.6	440.2	867	812	19.1	4"	649	12.6	4"	974	22.5	(2) 4"
EAW-VD9112ZA247I6-425AXSP04	-	471.1	351.6	400.3	810.6	-	470.2	354	401	802.1	654	17.7	4"	523	11.7	4"	785	24.9	4"
EAW-VD9114ZA247I6-625AXSP04	-	652.7	497.2	559.5	1086.6	-	649.8	497.4	558.4	1072.3	981	18.8	(2) 4"	785	15.3	4"	1177	26.4	(2) 4"
EAW-VD9114ZA247I6-525AXSP04	383.20	612.8	463.9	524.3	1032.2	387.3	610.3	463.9	522.9	1019.2	812	21.4	4"	649	14.1	4"	974	25.7	(2) 4"
EAW-VD9114ZA247I6-425AXSP04	345.60	559.6	420.9	476.9	954	349.5	557.4	421.2	475.8	943.8	654	20	4"	523	13.2	4"	785	28.1	4"
EAW-VD9116ZA247I6-625AXSP04	483.80	754.6	577.1	649	1249.2	486.8	750.1	576.3	645.9	1232.6	981	21.1	(2) 4"	785	16.8	4"	1177	29.6	(2) 4"
EAW-VD9116ZA247I6-525AXSP02	-	-	-	-	1120.7	-	-	-	-	1113.3	1635	14	(2) 4"	1308	9.2	(2) 4"	1962	16.4	(3) 4"
EAW-VD9116ZA247I6-425AXSP02	-	-	-	-	1027.5	-	-	-	-	1022.1	1308	12.5	(2) 4"	1046	8.2	(2) 4"	1570	17.5	(2) 4"
EAW-VD9118ZA247I6-625AXSP02	-	-	-	-	1341.3	-	-	-	-	1330.6	1962	13.6	(3) 4"	1570	11.1	(2) 4"	2354	19.1	(3) 4"
EAW-VD9118ZA247I6-525AXSP02	-	-	-	-	1274.4	-	-	-	-	1264	1635	15.1	(2) 4"	1308	9.9	(2) 4"	1962	18	(3) 4"
EAW-VD9118ZA247I6-425AXSP02	-	662.5	-	-	1168.3	-	668	-	-	1160.1	1308	13.6	(2) 4"	1046	9	(2) 4"	1570	19.1	(2) 4"
EAW-VD9120ZA247I6-625AXSP02	-	-	-	-	1503.1	-	-	-	-	1489.1	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD9120ZA247I6-525AXSP02	-	826.9	-	-	1427.4	-	829.4	-	-	1415.5	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD9120ZA247I6-425AXSP02	-	750.3	-	634.2	1309.8	-	753.5	-	639.6	1300.5	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD9102ZJ247I6-625AXSP16	-	-	-	-	158.9	-	-	-	-	157.3	242	16.4	3"	194	14	2"	291	22.9	3"
EAW-VD9102ZJ247I6-525AXSP16	-	-	-	-	148.6	-	-	-	-	147.2	194	19.1	2"	155	12.6	2"	232	26.8	2"
EAW-VD9102ZJ247I6-425AXSP16	-	78.3	-	-	137.3	-	78.7	-	-	136.1	157	17.8	2"	126	14.8	1-1/2"	189	25	2"
EAW-VD9104ZJ247I6-625AXSP12	-	196.9	-	169	327.3	-	195.9	-	168.4	322.8	327	21.1	3"	262	14	3"	392	29.7	3"
EAW-VD9104ZJ247I6-525AXSP12	-	183.4	138.9	157.1	308.9	-	182.7	139.1	156.5	305.1	266	20.4	3"	213	17.3	2"	320	28.7	3"
EAW-VD9104ZJ247I6-425AXSP12	104.50	169	127.1	144.3	288	105.6	168.3	127.3	143.9	284.4	218	23.9	2"	174	15.8	2"	262	28	3"
EAW-VD9106ZJ247I6-625AXSP08	-	293.2	-	251.5	487.6	-	291.7	-	250.5	480.9	484	22.3	3"	388	14.7	3"	581	27	4"
EAW-VD9106ZJ247I6-525AXSP08	-	274.8	207.7	234.9	462.8	-	273.3	208.1	234.4	456.5	400	20.9	3"	320	13.8	3"	480	29.4	3"
EAW-VD9106ZJ247I6-425AXSP08	156.20	252.7	190	215.7	430.8	157.9	251.6	190.4	215.2	425.5	327	19.9	3"	262	13.1	3"	392	27.9	3"
EAW-VD9108ZJ247I6-625AXSP06	-	391.9	-	336.2	652.4	-	389.9	-	334.9	643.4	654	19.8	4"	523	13.1	4"	785	27.9	4"
EAW-VD9108ZJ247I6-525AXSP06	-	369.4	279.5	316	621.7	-	367.5	279.5	314.8	613.2	545	19	4"	436	15.1	3"	654	26.7	4"
EAW-VD9108ZJ247I6-425AXSP06	207.50	335.8	252.8	286.7	572.7	209.8	334.5	252.9	286	565.7	436	20.9	3"	349	13.7	3"	523	25.7	4"
EAW-VD9110ZJ247I6-625AXSP06	322.80	499.8	383.6	430.5	823	323.6	495.8	382.3	427	810.7	654	23.7	4"	523	15.6	4"	785	33.3	4"
EAW-VD9110ZJ247I6-525AXSP04	-	447.7	-	381.6	762.5	-	447.4	-	382.1	754.2	812	18.1	4"	649	11.9	4"	974	21.1	(2) 4"
EAW-VD9110ZJ247I6-425AXSP04	-	407.8	304.3	346.8	703.8	-	407.8	306.4	347.4	696.4	654	16.7	4"	523	11	4"	785	23.4	4"
EAW-VD9112ZJ247I6-625AXSP04	-	585.6	-	501.6	975.1	-	582.6	-	500.4	961.8	981	18	(2) 4"	785	14.8	4"	1177	25.3	(2) 4"
EAW-VD9112ZJ247I6-525AXSP04	-	548.8	415.4	469.2	925.5	-	546.7	415.5	468.1	913	812	20.7	4"	649	13.6	4"	974	24.6	(2) 4"
EAW-VD9112ZJ247I6-425AXSP04	308.90	501.4	376.6	427.1	855.5	312.4	499.4	376.8	426.1	845.1	654	19.2	4"	523	12.7	4"	785	27	4"
EAW-VD9114ZJ247I6-625AXSP04	-	692.7	530.5	595.5	1145.6	-	688.2	528.8	592.3	1128.5	981	20.6	(2) 4"	785	16.5	4"	1177	28.9	(2) 4"
EAW-VD9114ZJ247I6-525AXSP04	411.70	650.1	494.5	557.2	1088	413.9	646.5	493.6	554.8	1073.1	812	23.2	4"	649	15.3	4"	974	28.2	(2) 4"
EAW-VD9114ZJ247I6-425AXSP02	-	-	-	-	940.2	-	-	-	-	935.1	1308	12.2	(2) 4"	1046	8	(2) 4"	1570	17.2	(2) 4"
EAW-VD9116ZJ247I6-625AXSP02	-	-	-	-	1250.3	-	-	-	-	1239.6	1962	13.5	(3) 4"	1570	11	(2) 4"	2354	19	(3) 4"
EAW-VD9116ZJ247I6-525AXSP02	-	-	-	-	1187.3	-	-	-	-	1176.3	1635	15	(2) 4"	1308	9.8	(2) 4"	1962	17.8	(3) 4"
EAW-VD9116ZJ247I6-425AXSP02	-	617.5	-	-	1089.1	-	621.4	-	-	1079.7	1308	13.5	(2) 4"	1046	8.9	(2) 4"	1570	19	(2) 4"
EAW-VD9118ZJ247I6-625AXSP02	-	-	-	-	1420.2	-	-	-	-	1404.5	1962	14.8	(3) 4"	1570	11.9	(2) 4"	2354	20.8	(3) 4"
EAW-VD9118ZJ247I6-525AXSP02	-	782.7	-	-	1348	-	785.1	-	-	1335.3	1635	16.3	(2) 4"	1308	10.7	(2) 4"	1962	19.6	(3) 4"
EAW-VD9118ZJ247I6-425AXSP02	-	709	-	-	1237.9	-	711.9	-	-	1227	1308	14.8	(2) 4"	1046	9.7	(2) 4"	1570	20.8	(2) 4"
EAW-VD9102PA247I6-625AXSP16	-	-	-	-	128.1	-	-	-	-	127.5	182	17.4	2"	145	11.5	2"	218	24.5	2"
EAW-VD9102PA247I6-525AXSP16	-	68.1	-	-	120.3	-	69	-	-	119.8	145	16.2	2"	116	13.2	1-1/2"	174	22.8	2"
EAW-VD9102PA247I6-425AXSP16	-	63.6	-	-	113.3	-	64.4	-	-	112.9	121	18.2	1-1/2"	97	12	1-1/2"	145	21.9	2"
EAW-VD9104PA247I6-625AXSP12	-	156.5	118.2	133.7	263.5	-	156.7	119	134.1	261.3	242	18.6	3"	194	15.3	2"	291	26.1	3"
EAW-VD9104PA247I6-525AXSP12	-	145.1	108.9	123.8	248	90.6	145.3	109.7	124.1	245.9	194	21.2	2"	155	14	2"	232	29.8	2"
EAW-VD9104PA247I6-425AXSP08	-	126.5	-	-	225.8	-	128.2	-	-	224.8	242	12.8	3"	194	11.4	2"	291	17.9	3"
EAW-VD9106PA247I6-625AXSP08	-	234.1	176.8	200	394.3	-	234.4	178	200.8	391.1	363	18.7	3"	291	12.4	3"	436	26.3	3"
EAW-VD9106PA247I6-525AXSP08	-	221.7	166.5	189.3	378.1	-	222.1	167.8	189.6	375.3	303	18	3"	242	11.9	3"	363	25.2	3"
EAW-VD9106PA247I6-425AXSP08	123.10	202.7	151.1	172.2	349.9	125.3	202.9	152.3	173	347.6	242	17.4	3"	194	14.4	2"	291	24.3	3"
EAW-VD9108PA247I6-625AXSP06	-	311.3	235.1	265.9	525.1	-	311.7	236.7	267	520.8	484	20	3"	388	13.2	3"	581	23.9	4"
EAW-VD9108PA247I6-525AXSP06	-	293.4	220.1	249.9	500.7	-	293.6	222	250.9	497.1	400	18.6	3"	320	12.3	3"	480	26.2	3"
EAW-VD9108PA247I6-425AXSP06	160.60	265.1	197.6	225.3	458.7	163.7	265.9	199.3	226.1	455.2	315	17.5	3"	252	11.5	3"	378	24.5	3"
EAW-VD9110PA247I6-625AXSP06	252.90	398.6	303.6	341.5	663.6	255.4	397.3	304.1	341.3	657.3	484	23.5	3"	388	15.4	3"	581	28.8	4"
EAW-VD9110PA247I6-525AXSP04	-	357.3	-	303.3	618.3	-	359.4	-	305.7	613.9	606	14.9	4"	484	12.8	3"	727	21	4"
EAW-VD9110PA247I6-425AXSP04	-	326.1	240.7	275.8	570.8	-	327.9	243.8	278.4	567.2	484	17.1	3"	388	11.2	3"	581	19.8	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-VD9112PA247I6-625AXSP04	-	464.3	350.5	397.1	783.8	-	465	353.5	398.3	777.4	727	18.2	4"	581	12	4"	872	25.6	4"
EAW-VD9112PA247I6-525AXSP04	-	440.1	330.2	374.9	751.1	-	440.3	332.4	376.3	745.6	606	17.2	4"	484	14.3	3"	727	24.2	4"
EAW-VD9112PA247I6-425AXSP04	243.00	401.2	299.3	341.2	694.5	247.8	402.4	301.8	342.2	689	484	19.4	3"	388	12.7	3"	581	23.1	4"
EAW-VD9114PA247I6-625AXSP04	347.60	551.3	418.8	472.1	922.3	352.3	550.5	420.3	472.6	914.7	727	20.5	4"	581	13.5	4"	872	28.8	4"
EAW-VD9114PA247I6-525AXSP02	-	-	-	-	823.2	-	-	-	-	822.5	1211	10.8	(2) 4"	969	7.1	(2) 4"	1453	15.3	(2) 4"
EAW-VD9114PA247I6-425AXSP02	-	-	-	-	756.7	-	-	-	-	757.6	969	10	(2) 4"	775	9.4	4"	1163	14.1	(2) 4"
EAW-VD9116PA247I6-625AXSP02	-	-	-	-	1000.2	-	-	-	-	997.7	1453	13	(2) 4"	1163	8.5	(2) 4"	1744	18.3	(2) 4"
EAW-VD9116PA247I6-525AXSP02	-	-	-	-	954.3	-	-	-	-	951.9	1211	12	(2) 4"	969	7.9	(2) 4"	1453	16.9	(2) 4"
EAW-VD9116PA247I6-425AXSP02	-	489.9	-	-	879.1	-	497.1	-	-	876.9	969	11.2	(2) 4"	775	10.1	4"	1163	15.7	(2) 4"
EAW-VD9118PA247I6-625AXSP02	-	-	-	-	1136.8	-	-	-	-	1132.3	1453	14.1	(2) 4"	1163	9.3	(2) 4"	1744	19.9	(2) 4"
EAW-VD9118PA247I6-525AXSP02	-	620.2	-	-	1085.7	-	626.3	-	-	1081.3	1211	13.1	(2) 4"	969	8.7	(2) 4"	1453	18.5	(2) 4"
EAW-VD9118PA247I6-425AXSP02	-	563.8	-	475.5	1000.1	-	569.5	-	482.3	995.9	969	12.3	(2) 4"	775	10.9	4"	1163	17.3	(2) 4"
EAW-VD9120PA247I6-625AXSP02	-	743.3	-	-	1274.3	-	748.1	-	-	1267.5	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD9120PA247I6-525AXSP02	-	701.3	-	594.5	1218.1	-	705.7	-	600.4	1209.7	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD9120PA247I6-425AXSP02	-	638.2	470.5	539.9	1121.9	-	643.1	477.7	545.3	1115.3	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD9102PJ247I6-625AXSP16	-	-	-	-	137.4	-	-	-	-	136.6	182	18.4	2"	145	12.1	2"	218	25.9	2"
EAW-VD9102PJ247I6-525AXSP16	-	73.9	-	-	128.9	-	74.5	-	-	128	145	17.3	2"	116	13.8	1-1/2"	174	24.2	2"
EAW-VD9102PJ247I6-425AXSP16	-	68.9	-	58.2	121.3	-	69.4	-	58.8	120.7	121	19.3	1-1/2"	97	12.7	1-1/2"	145	23.3	2"
EAW-VD9104PJ247I6-625AXSP12	-	168.6	128.1	144.5	281.9	-	168.2	128.5	144.4	279.1	242	20.2	3"	194	16.3	2"	291	28.3	3"
EAW-VD9104PJ247I6-525AXSP12	97.00	156.1	117.8	133.4	264.8	98.3	156	118.2	133.4	262.2	194	22.7	2"	155	15	2"	232	31.9	2"
EAW-VD9104PJ247I6-425AXSP08	-	137.1	-	115.8	241.5	-	138.1	-	117.1	240.3	242	13.8	3"	194	12.1	2"	291	19.3	3"
EAW-VD9106PJ247I6-625AXSP08	-	252.2	191.7	216.2	421.9	-	251.7	192.2	216	417.6	363	20.3	3"	291	13.4	3"	436	28.5	3"
EAW-VD9106PJ247I6-525AXSP08	148.60	238.7	180.2	203.8	403.6	150.4	238.4	180.7	203.9	399.6	303	19.5	3"	242	12.9	3"	363	27.4	3"
EAW-VD9106PJ247I6-425AXSP06	-	206	152.2	174.4	360	-	206.7	154	175.7	357.7	315	15.2	3"	252	10	3"	378	21.3	3"
EAW-VD9108PJ247I6-625AXSP06	-	335.9	254.8	287.4	561.9	-	335.1	255.5	287.6	555.5	484	21.5	3"	388	14.2	3"	581	26.1	4"
EAW-VD9108PJ247I6-525AXSP06	196.00	315.4	238.3	269.7	534.6	198.9	315.1	239	269.8	529.3	400	20.1	3"	320	13.3	3"	480	28.3	3"
EAW-VD9108PJ247I6-425AXSP04	-	271.3	-	229	479.3	-	273.7	-	231.7	476.2	484	15.8	3"	388	10.4	3"	581	18	4"
EAW-VD9110PJ247I6-625AXSP04	-	408.8	-	348.7	692.2	-	409.1	-	350.1	685.3	727	17.2	4"	581	11.3	4"	872	24.2	4"
EAW-VD9110PJ247I6-525AXSP04	-	385.6	288.5	328.1	660.3	-	386.5	291.1	329.5	655.6	606	16.2	4"	484	13.6	3"	727	22.8	4"
EAW-VD9110PJ247I6-425AXSP04	-	351.3	261.4	298.5	610.2	-	352.3	263.6	299.9	605.2	484	18.4	3"	388	12.1	3"	581	21.6	4"
EAW-VD9112PJ247I6-625AXSP04	-	501.2	379.9	429.3	838.7	-	500.1	381.6	429	830.3	727	19.7	4"	581	13	4"	872	27.8	4"
EAW-VD9112PJ247I6-525AXSP04	294.10	473.2	356.8	403.9	801.9	297.9	472.7	358.5	404.1	794	606	18.8	4"	484	15.3	3"	727	26.4	4"
EAW-VD9112PJ247I6-425AXSP02	-	-	-	-	684.5	-	-	-	-	683.9	969	9.7	(2) 4"	775	9.1	4"	1163	13.6	(2) 4"
EAW-VD9114PJ247I6-625AXSP04	378.20	593.2	452.4	509.4	986.8	381.1	591.1	452.9	508.1	975.6	727	22.3	4"	581	14.7	4"	872	31.3	4"
EAW-VD9114PJ247I6-525AXSP02	-	-	-	-	883.7	-	-	-	-	880.5	1211	11.7	(2) 4"	969	7.7	(2) 4"	1453	16.5	(2) 4"
EAW-VD9114PJ247I6-425AXSP02	-	452.6	-	-	812.8	-	459.1	-	-	810.6	969	10.9	(2) 4"	775	10	4"	1163	15.4	(2) 4"
EAW-VD9116PJ247I6-625AXSP02	-	-	-	-	1075.2	-	-	-	-	1068.9	1453	14	(2) 4"	1163	9.2	(2) 4"	1744	19.7	(2) 4"
EAW-VD9116PJ247I6-525AXSP02	-	584.5	-	-	1024.1	-	590.3	-	-	1018.7	1211	13	(2) 4"	969	8.6	(2) 4"	1453	18.3	(2) 4"
EAW-VD9116PJ247I6-425AXSP02	-	530.9	-	448.2	942.2	-	536.1	-	453.8	936.5	969	12.2	(2) 4"	775	10.8	4"	1163	17.2	(2) 4"
EAW-VD9118PJ247I6-625AXSP02	-	712.8	-	-	1220.2	-	715.9	-	-	1211.4	1453	15.3	(2) 4"	1163	10.1	(2) 4"	1744	21.5	(2) 4"
EAW-VD9118PJ247I6-525AXSP02	-	671.1	-	569.6	1163.2	-	675.4	-	574.5	1155.3	1211	14.3	(2) 4"	969	9.4	(2) 4"	1453	20.1	(2) 4"
EAW-VD9118PJ247I6-425AXSP02	-	610.4	450	516.3	1070	-	613.8	456.5	520.3	1063.3	969	13.5	(2) 4"	775	11.6	4"	1163	18.9	(2) 4"
EAW-VD91S1MA247I6-625AXSP16	-	-	-	-	73.8	-	-	-	-	73.3	109	18.1	1-1/2"	87	11.9	1-1/2"	131	25.5	1-1/2"
EAW-VD91S1MA247I6-525AXSP16	-	-	-	-	70.1	-	-	-	-	69.6	97	16.6	1-1/2"	78	10.9	1-1/2"	116	23.3	1-1/2"
EAW-VD91S1MA247I6-425AXSP16	-	36.7	-	-	64.7	-	36.9	-	-	64.3	73	16.4	1-1/2"	58	10.8	1-1/2"	87	23	1-1/2"
EAW-VD91S2MA247I6-625AXSP12	-	90.7	-	77.7	152.1	-	90.6	-	77.7	150.5	157	19.8	2"	126	15.7	1-1/2"	189	27.8	2"
EAW-VD91S2MA247I6-525AXSP12	-	86.5	65.4	73.9	146.1	-	86.3	65.5	73.8	144.5	121	22.7	1-1/2"	97	15	1-1/2"	145	28.5	2"
EAW-VD91S2MA247I6-425AXSP08	-	72.8	-	-	129.4	-	73.6	-	-	128.7	157	13.9	2"	126	11.8	1-1/2"	189	19.6	2"
EAW-VD91S3MA247I6-625AXSP08	-	134.3	-	114.8	225.5	-	134	-	115	223.2	230	21.1	2"	184	13.9	2"	276	24.1	3"
EAW-VD91S3MA247I6-525AXSP08	-	127.2	95.6	108.5	216	-	126.9	96.1	108.6	213.7	194	19.7	2"	155	13	2"	232	27.7	2"
EAW-VD91S3MA247I6-425AXSP08	-	116.6	87.2	99.2	200.5	-	116.6	87.6	99.4	198.5	157	18.5	2"	126	14.8	1-1/2"	189	26	2"
EAW-VD91S4MA247I6-625AXSP08	118.00	184.3	140.9	158.2	305	118.7	183.1	140.7	157.6	301.1	230	25.7	2"	184	16.9	2"	276	30.6	3"
EAW-VD91S4MA247I6-525AXSP06	-	167.8	126	143.1	285.4	-	167.6	126.8	143.3	282.4	254	16.8	3"	204	14.1	2"	305	23.5	3"
EAW-VD91S4MA247I6-425AXSP06	-	153.4	114.5	130.4	263.9	-	153.2	115.1	130.5	261.3	206	19.5	2"	165	12.8	2"	247	23	3"
EAW-VD91S5MA247I6-625AXSP06	147.50	231	176.6	198.3	383.5	148.6	230	176.4	197.7	378.6	315	20.9	3"	252	13.8	3"	378	29.3	3"
EAW-VD91S5MA247I6-525AXSP04	-	204.9	-	-	353.1	-	205.5	-	-	349.8	388	15.4	3"	310	10.1	3"	465	21.6	3"
EAW-VD91S5MA247I6-425AXSP04	-	187.5	-	158.9	327.5	-	188.3	-	160	324.7	315	14.5	3"	252	9.5	3"	378	20.3	3"
EAW-VD91S6MA247I6-625AXSP04	-	269.7	-	230.6	453.2	-	269.4	-	231	447.9	472	19	3"	378	12.5	3"	567	22.9	4"
EAW-VD91S6MA247I6-525AXSP04	-	252.1	189.6	214.9	429.3	-	252.1	190.4	215.2	424.7	388	17.7	3"	310	11.7	3"	465	24.9	3"
EAW-VD91S6MA247I6-425AXSP04	-	231.2	172.7	196.7	398.2	-	230.9	173.6	196.8	394.2	315	16.8	3"	252	11.1	3"	378	23.6	3"
EAW-FD91S1WK320P7-625AXSP16	-	58.3	44.4	50	97.1	-	57.9	44.3	49.8	95.6	91	23.5	2"	73	15.5	2"	109	33	2"
EAW-FD91S1WK320P7-525AXSP16	-	53.4	40.4	45.7	90.2	33.6	53.2	40.4	45.5	88.9	73	22.4	2"	58	17.2	1-1/2"	87	31.4	2"
EAW-FD91S1WK320P7-425AXSP12	-	46.7	-	39.6	81.2	-	46.7	-	39.7	80.3	79	17.6	2"	63	14.5	1-1/2"	94	24.8	2"
EAW-FD91S2WK320P7-625AXSP08	-	116.3	88.5	99.7	193.8	-	115.5	88.3	99.1	190.8	182	20.3	3"	145	13.4	3"	218	28.5	3"
EAW-FD91S2WK320P7-525AXSP08	-	108.7	82.1	92.9	183.2	-	107.9	82.1	92.5	180.6	151	19.5	3"	121	12.9	3"	182	27.4	3"
EAW-FD91S2WK320P7-425AXSP08	60.40	98	73.7	83.6	167.2	61	97.5	73.6	83.3	164.9	121	18.9	3"	97	15.4	2"	145	26.5	3"
EAW-FD91S3WK320P7-625AXSP06	112.30	176	134.4	151.1	291.7	112.8	174.6	133.9	150.1	287.2	242	23.5	3"	194	15.4	3"	291	28.8	4"
EAW-FD91S3WK320P7-525AXSP04	-	155.7	-	-	267.8	-	155.9	-	-	264.8	303	14.9	4"	242	12.8	3"	363	21	4"
EAW-FD91S3WK320P7-425AXSP04	-	140.2	-	118.7	244	-	140.3	-	119.3	241.5	242	17.1	3"	194	11.2	3"	291	19.8	4"
EAW-FD91S4WK320P7-625AXSP04	-	230.8	175.4	197.7	385.3	-	229.3	175.4	197	379.4	363	19.7	4"	291	13	4"	436	27.8	4"
EAW-FD91S4WK320P7-525AXSP04	-	215.5	162.9	184.1	364	-	214.4	163	183.7	359	303	18.8	4"	242	15.3	3"	363	26.4	4"
EAW-FD91S4WK320P7-425AXSP04	119.60	194.1	145.7	165.4	332	120.7	193.2	146	164.9	327.6	242	20.9	3"	194	13.8	3"	291	25.2	4"
EAW-FD91S5WK320P7-625AXSP04	189.30	294.4	225.5	253.3	486.8	189.6	291.7	224.5	251.2	478.7	363	23.6	4"	291	15.5	4"	436	33.1	4"
EAW-FD91S5WK320P7-525AXSP02	-	-	-	-	433.5	-	-	-	-	429.4	606	12.4	(2) 4"	484	8.2	(2) 4"	727	17.4	(2) 4"
EAW-FD91S5WK320P7-425AXSP02	-	-	-	-	393.5	-	-	-	-	390.3	484	11.6	(2) 4"	388	10.4	4"	581	16.3	(2) 4"
EAW-FD91S6WK320P7-625AXSP02	-	-	-	-	561	-	-	-	-	554.5	727	15.3	(2) 4"	581	10.1	(2) 4"	872	21.5	(2) 4"
EAW-FD91S6WK320P7-525AXSP02	-	305.8	-	-	528.6	-	306.4	-	-	522.1	606	14.3	(2) 4"	484	9.4	(2) 4"	727	20.1	(2) 4"
EAW-FD91S6WK320P7-425AXSP02	-	274.7	-	232.7	480.1	-	275.6	-	234	475.4	484	13.5	(2) 4"	388	11.6	4"	581	18.9	(2) 4"
EAW-FD15S1ZB370K4-625AXSP16	-	77.1	58.3	65.9	129.7	-	77.3	58.7	66.1	128.9	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB370K4-525AXSP16	-	71.8	53.9	61.2	122.6	44.9	71.9	54.3	61.4	121.7	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB370K4-425AXSP12	-	65	-	54.9	114.6	-	65.6	-	55.7	114	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB550K4-625AXSP16	-	84.5	63.6	72.1	142.6	-	84.7	64.3	72.5	141.9	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB550K4-525AXSP16	48.10	78.6	58.8	66.8	134.6	49	78.8	59.4	67.2	133.9	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB550K4-425AXSP12	-	71.1	52.1	60	125.7	-	71.9	53.2	60.8	125.3	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB750K4-625AXSP16	-	88.8	66.9	75.9	150.3	56.1	89.2	67.7	76.4	149.6	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB750K4-525AXSP12	-	80.7	-	68.2	141.2	-	81.6	-	69.3	141	133	15.5	3"	107	14	2"	160	21.7	3"
EAW-FD15S1ZB750K4-425AXSP12	-	75.2	55	63.4	133	-	76	56.2	64.3	132.9	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB370K5-625AXSP16	-	77.1	58.3	65.9	129.7	-	77.3	58.7	66.1	128.9	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB370K5-525AXSP16	-	71.8	53.9	61.2	122.6	44.9	71.9	54.3	61.4	121.7	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB370K5-425AXSP12	-	65	-	54.9	114.6	-	65.6	-	55.7	114	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB550K5-625AXSP16	-	84.5	63.6	72.1	142.6	-	84.7	64.3	72.5	141.9	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB550K5-525AXSP16	48.10	78.6	58.8	66.8	134.6	49	78.8	59.4	67.2	133.9	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB550K5-425AXSP12	-	71.1	52.1	60	125.7	-	71.9	53.2	60.8	125.3	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB750K5-625AXSP16	-	88.8	66.9	75.9	150.3	56.1	89.2	67.7	76.4	149.6	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB750K5-525AXSP12	-	80.7	-	68.2	141.2	-	81.6	-	69.3	141	133	15.5	3"	107	14	2"	160	21.7	3"
EAW-FD15S1ZB750K5-425AXSP12	-	75.2	55	63.4	133	-	76	56.2	64.3	132.9	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB370C4-625AXSP16	-	78.2	59.2	66.9	131.7	-	78.5	59.7	67.3	131.2	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB370C4-525AXSP16	45.10	73.4	55.1	62.6	125.6	46	73.8	55.7	63	124.9	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB370C4-425AXSP12	-	66.9	-	56.5	118.1	-	67.6	-	57.3	117.7	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB550C4-625AXSP16	-	87.5	66.1	74.8	148.2	-	88.1	66.8	75.4	147.8	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB550C4-525AXSP12	-	79.7	-	67.5	139.4	-	80.7	-	68.5	139.2	133	15.5	3"	107	14	2"	160	21.7	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1ZB550C4-425AXSP12	-	74.3	54.4	62.7	131.4	-	75.1	55.5	63.5	131.2	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB370C5-625AXSP16	-	78.2	59.2	66.9	131.7	-	78.5	59.7	67.3	131.2	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB370C5-525AXSP16	45.10	73.4	55.1	62.6	125.6	46	73.8	55.7	63	124.9	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB370C5-425AXSP12	-	66.9	-	56.5	118.1	-	67.6	-	57.3	117.7	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB550C5-625AXSP16	-	87.5	66.1	74.8	148.2	-	88.1	66.8	75.4	147.8	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB550C5-525AXSP12	-	79.7	-	67.5	139.4	-	80.7	-	68.5	139.2	133	15.5	3"	107	14	2"	160	21.7	3"
EAW-FD15S1ZB550C5-425AXSP12	-	74.3	54.4	62.7	131.4	-	75.1	55.5	63.5	131.2	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB370K8-625AXSP16	-	77.1	58.3	65.9	129.7	-	77.3	58.7	66.1	128.9	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB370K8-525AXSP16	-	71.8	53.9	61.2	122.6	44.9	71.9	54.3	61.4	121.7	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB370K8-425AXSP12	-	65	-	54.9	114.6	-	65.6	-	55.7	114	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB550K8-625AXSP16	-	84.5	63.6	72.1	142.6	-	84.7	64.3	72.5	141.9	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB550K8-525AXSP16	48.10	78.6	58.8	66.8	134.6	49	78.8	59.4	67.2	133.9	97	22.7	2"	78	14.9	2"	116	31.8	2"
EAW-FD15S1ZB550K8-425AXSP12	-	71.1	52.1	60	125.7	-	71.9	53.2	60.8	125.3	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S1ZB750K8-625AXSP16	-	88.8	66.9	75.9	150.3	56.1	89.2	67.7	76.4	149.6	121	19.9	3"	97	16.3	2"	145	28	3"
EAW-FD15S1ZB750K8-525AXSP12	-	80.7	-	68.2	141.2	-	81.6	-	69.3	141	133	15.5	3"	107	14	2"	160	21.7	3"
EAW-FD15S1ZB750K8-425AXSP12	-	75.2	55	63.4	133	-	76	56.2	64.3	132.9	109	19	2"	87	12.5	2"	131	21	3"
EAW-FD15S2ZB370K4-625AXSP08	-	153.5	116	131.2	258.6	-	153.9	116.9	131.7	256.8	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB370K4-525AXSP08	-	145.3	109	123.8	247.8	-	145.6	109.9	124.4	246.1	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB370K4-425AXSP08	82.10	135.3	100.9	115	233.4	83.8	135.6	101.9	115.5	231.9	164	18.3	3"	131	12.1	3"	196	25.8	3"
EAW-FD15S2ZB550K4-625AXSP08	-	168.2	126.9	143.7	284.5	-	168.8	128	144.4	282.7	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB550K4-525AXSP08	97.40	159.1	119.3	135.5	272.5	99.3	159.8	120.4	136.3	271.1	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB550K4-425AXSP06	-	141.1	103.5	119.1	249.7	-	142.7	105.6	120.7	249.1	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB750K4-625AXSP08	-	176.8	133.3	151.1	299.9	-	177.7	134.7	152.1	298.5	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB750K4-525AXSP08	102.40	167.7	125.7	142.8	287.7	104.8	168.7	126.9	143.9	286.9	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB750K4-425AXSP06	-	149.2	109.2	125.8	264.3	-	150.9	111.5	127.6	264	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB370K5-625AXSP08	-	153.5	116	131.2	258.6	-	153.9	116.9	131.7	256.8	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB370K5-525AXSP08	-	145.3	109	123.8	247.8	-	145.6	109.9	124.4	246.1	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB370K5-425AXSP08	82.10	135.3	100.9	115	233.4	83.8	135.6	101.9	115.5	231.9	164	18.3	3"	131	12.1	3"	196	25.8	3"
EAW-FD15S2ZB550K5-625AXSP08	-	168.2	126.9	143.7	284.5	-	168.8	128	144.4	282.7	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB550K5-525AXSP08	97.40	159.1	119.3	135.5	272.5	99.3	159.8	120.4	136.3	271.1	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB550K5-425AXSP06	-	141.1	103.5	119.1	249.7	-	142.7	105.6	120.7	249.1	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB750K5-625AXSP08	-	176.8	133.3	151.1	299.9	-	177.7	134.7	152.1	298.5	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB750K5-525AXSP08	102.40	167.7	125.7	142.8	287.7	104.8	168.7	126.9	143.9	286.9	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB750K5-425AXSP06	-	149.2	109.2	125.8	264.3	-	150.9	111.5	127.6	264	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB370C4-625AXSP08	-	155.9	117.8	133.2	262.8	-	156.7	119	134	261.5	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB370C4-525AXSP08	-	148.7	111.6	126.8	253.9	93.3	149.4	112.7	127.6	252.8	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB370C4-425AXSP06	-	132.9	-	112.2	234.7	-	134.3	-	113.7	234	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB550C4-625AXSP08	-	174.6	131.5	149	295.7	-	175.4	133	150.1	294.6	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB550C4-525AXSP08	101.30	165.7	124	141.1	284.4	103.6	166.6	125.4	142.1	283.2	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB550C4-425AXSP06	-	147.5	107.9	124.3	261.4	-	149.1	110.3	126.2	261.1	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB370C5-625AXSP08	-	155.9	117.8	133.2	262.8	-	156.7	119	134	261.5	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB370C5-525AXSP08	-	148.7	111.6	126.8	253.9	93.3	149.4	112.7	127.6	252.8	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB370C5-425AXSP06	-	132.9	-	112.2	234.7	-	134.3	-	113.7	234	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB550C5-625AXSP08	-	174.6	131.5	149	295.7	-	175.4	133	150.1	294.6	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB550C5-525AXSP08	101.30	165.7	124	141.1	284.4	103.6	166.6	125.4	142.1	283.2	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB550C5-425AXSP06	-	147.5	107.9	124.3	261.4	-	149.1	110.3	126.2	261.1	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB370K8-625AXSP08	-	153.5	116	131.2	258.6	-	153.9	116.9	131.7	256.8	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB370K8-525AXSP08	-	145.3	109	123.8	247.8	-	145.6	109.9	124.4	246.1	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB370K8-425AXSP08	82.10	135.3	100.9	115	233.4	83.8	135.6	101.9	115.5	231.9	164	18.3	3"	131	12.1	3"	196	25.8	3"
EAW-FD15S2ZB550K8-625AXSP08	-	168.2	126.9	143.7	284.5	-	168.8	128	144.4	282.7	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB550K8-525AXSP08	97.40	159.1	119.3	135.5	272.5	99.3	159.8	120.4	136.3	271.1	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB550K8-425AXSP06	-	141.1	103.5	119.1	249.7	-	142.7	105.6	120.7	249.1	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S2ZB750K8-625AXSP08	-	176.8	133.3	151.1	299.9	-	177.7	134.7	152.1	298.5	242	20.8	3"	194	13.7	3"	291	24.9	4"
EAW-FD15S2ZB750K8-525AXSP08	102.40	167.7	125.7	142.8	287.7	104.8	168.7	126.9	143.9	286.9	200	19.4	3"	160	12.8	3"	240	27.2	3"
EAW-FD15S2ZB750K8-425AXSP06	-	149.2	109.2	125.8	264.3	-	150.9	111.5	127.6	264	218	15.9	3"	174	10.4	3"	262	18.8	4"
EAW-FD15S3ZB370K4-625AXSP06	-	234	177.7	200.5	391.6	-	234.3	178.8	200.9	388.5	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB370K4-525AXSP06	138.60	222.8	168.2	190.4	377.7	140.8	222.9	169.2	190.8	374.5	272	19.2	4"	218	15.2	3"	327	27	4"
EAW-FD15S3ZB370K4-425AXSP04	-	192.4	-	162.2	339.4	-	194.2	-	164.5	338.5	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB550K4-625AXSP06	160.90	256.5	194.4	219.4	430.5	163.5	257	195.8	220.3	427.7	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB550K4-525AXSP04	-	228.6	-	193.3	399.8	-	230.9	-	196	398.8	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB550K4-425AXSP04	-	210.4	154	177.4	372.2	-	212.4	157.1	180	371.8	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB750K4-625AXSP04	-	253.9	-	-	439.6	-	257	-	-	439.4	490	13.1	(2) 4"	392	11.5	4"	589	18.3	(2) 4"
EAW-FD15S3ZB750K4-525AXSP04	-	240.8	-	203.6	422.3	-	243.9	-	206.8	421.9	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB750K4-425AXSP04	-	222	162.6	187.2	394.4	-	224.7	166	190.1	394.1	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB370K5-625AXSP06	-	234	177.7	200.5	391.6	-	234.3	178.8	200.9	388.5	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB370K5-525AXSP06	138.60	222.8	168.2	190.4	377.7	140.8	222.9	169.2	190.8	374.5	272	19.2	4"	218	15.2	3"	327	27	4"
EAW-FD15S3ZB370K5-425AXSP04	-	192.4	-	162.2	339.4	-	194.2	-	164.5	338.5	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB550K5-625AXSP06	160.90	256.5	194.4	219.4	430.5	163.5	257	195.8	220.3	427.7	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB550K5-525AXSP04	-	228.6	-	193.3	399.8	-	230.9	-	196	398.8	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB550K5-425AXSP04	-	210.4	154	177.4	372.2	-	212.4	157.1	180	371.8	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB750K5-625AXSP04	-	253.9	-	-	439.6	-	257	-	-	439.4	490	13.1	(2) 4"	392	11.5	4"	589	18.3	(2) 4"
EAW-FD15S3ZB750K5-525AXSP04	-	240.8	-	203.6	422.3	-	243.9	-	206.8	421.9	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB750K5-425AXSP04	-	222	162.6	187.2	394.4	-	224.7	166	190.1	394.1	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB370C4-625AXSP06	-	237.7	180.4	203.6	398	152.2	238.5	181.9	204.5	395.6	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB370C4-525AXSP06	141.90	228.1	172	194.8	387	144.1	228.8	173.3	195.7	384.8	272	19.2	4"	218	15.2	3"	327	27	4"
EAW-FD15S3ZB370C4-425AXSP04	-	197.9	-	167	349.8	-	200.1	-	169.6	349.4	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB550C4-625AXSP06	166.70	266.3	201.6	227.9	448	169.8	267.1	203.2	228.8	445.7	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB550C4-525AXSP04	-	237.9	-	201.3	417	-	240.9	-	204.3	417.1	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB550C4-425AXSP04	-	219.5	160.7	185.1	389.6	-	222	164.2	187.9	389.1	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB370C5-625AXSP06	-	237.7	180.4	203.6	398	152.2	238.5	181.9	204.5	395.6	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB370C5-525AXSP06	141.90	228.1	172	194.8	387	144.1	228.8	173.3	195.7	384.8	272	19.2	4"	218	15.2	3"	327	27	4"
EAW-FD15S3ZB370C5-425AXSP04	-	197.9	-	167	349.8	-	200.1	-	169.6	349.4	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB550C5-625AXSP06	166.70	266.3	201.6	227.9	448	169.8	267.1	203.2	228.8	445.7	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB550C5-525AXSP04	-	237.9	-	201.3	417	-	240.9	-	204.3	417.1	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB550C5-425AXSP04	-	219.5	160.7	185.1	389.6	-	222	164.2	187.9	389.1	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB370K8-625AXSP06	-	234	177.7	200.5	391.6	-	234.3	178.8	200.9	388.5	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB370K8-525AXSP06	138.60	222.8	168.2	190.4	377.7	140.8	222.9	169.2	190.8	374.5	272	19.2	4"	218	15.2	3"	327	27	4"
EAW-FD15S3ZB370K8-425AXSP04	-	192.4	-	162.2	339.4	-	194.2	-	164.5	338.5	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB550K8-625AXSP06	160.90	256.5	194.4	219.4	430.5	163.5	257	195.8	220.3	427.7	327	20	4"	262	13.2	4"	392	28.2	4"
EAW-FD15S3ZB550K8-525AXSP04	-	228.6	-	193.3	399.8	-	230.9	-	196	398.8	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB550K8-425AXSP04	-	210.4	154	177.4	372.2	-	212.4	157.1	180	371.8	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S3ZB750K8-625AXSP04	-	253.9	-	-	439.6	-	257	-	-	439.4	490	13.1	(2) 4"	392	11.5	4"	589	18.3	(2) 4"
EAW-FD15S3ZB750K8-525AXSP04	-	240.8	-	203.6	422.3	-	243.9	-	206.8	421.9	406	15.7	4"	325	10.3	4"	487	17.7	(2) 4"
EAW-FD15S3ZB750K8-425AXSP04	-	222	162.6	187.2	394.4	-	224.7	166	190.1	394.1	327	14.2	4"	262	9.4	4"	392	20	4"
EAW-FD15S4ZB370K4-625AXSP04	-	306.6	231.3	262	516.5	-	307.1	233.6	263.1	513	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB370K4-525AXSP04	-	290.5	217.7	247.5	495.6	-	291.2	219.9	248.5	492.2	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB370K4-425AXSP04	162.40	267.8	199.5	227.8	463.2	165.6	269	201.5	228.9	460.3	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB550K4-625AXSP04	-	335.5	253	286.5	568.3	-	337.1	255.6	288.3	564.7	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB550K4-525AXSP04	194.50	317.7	238.2	270.9	545.1	198.7	319.1	240.3	272.5	542.2	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB550K4-425AXSP04	176.90	292.8	217.9	248.8	-	180.8	294.2	220.5	250.5	-	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB750K4-625AXSP04	-	353.1	265.7	301.2	599.1	-	354.9	268.6	303.7	596.3	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S4ZB750K4-525AXSP04	204.50	335	250.9	285.2	575.3	209.2	337.4	253.9	287.7	573.8	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB750K4-425AXSP02	-	-	-	-	491.6	-	-	-	-	494.4	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.3	(2) 4"
EAW-FD15S4ZB370K5-625AXSP04	-	306.6	231.3	262	516.5	-	307.1	233.6	263.1	513	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB370K5-525AXSP04	-	290.5	217.7	247.5	495.6	-	291.2	219.9	248.5	492.2	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB370K5-425AXSP04	162.40	267.8	199.5	227.8	463.2	165.6	269	201.5	228.9	460.3	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB550K5-625AXSP04	-	335.5	253	286.5	568.3	-	337.1	255.6	288.3	564.7	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB550K5-525AXSP04	194.50	317.7	238.2	270.9	545.1	198.7	319.1	240.3	272.5	542.2	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB550K5-425AXSP04	176.90	292.8	217.9	248.8	-	180.8	294.2	220.5	250.5	-	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB750K5-625AXSP04	-	353.1	265.7	301.2	599.1	-	354.9	268.6	303.7	596.3	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB750K5-525AXSP04	204.50	335	250.9	285.2	575.3	209.2	337.4	253.9	287.7	573.8	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB750K5-425AXSP02	-	-	-	-	491.6	-	-	-	-	494.4	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.3	(2) 4"
EAW-FD15S4ZB370C4-625AXSP04	-	311	234.8	265.7	524.9	-	312.5	237.6	267.7	522.4	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB370C4-525AXSP04	-	297.3	222.9	253.2	507.8	-	298.8	225.4	254.8	505.6	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB370C4-425AXSP04	166.90	275.5	205.3	234.2	477.5	170.5	276.8	207.8	235.7	474.5	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB550C4-625AXSP04	-	348.2	262.2	297.2	590.6	-	350.3	265.7	299.8	588.4	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB550C4-525AXSP04	202.20	331.4	248	281.8	568.8	206.8	333.2	250.9	284.2	566.3	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB550C4-425AXSP02	-	-	-	-	485.8	-	-	-	-	489.2	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.3	(2) 4"
EAW-FD15S4ZB370C5-625AXSP04	-	311	234.8	265.7	524.9	-	312.5	237.6	267.7	522.4	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB370C5-525AXSP04	-	297.3	222.9	253.2	507.8	-	298.8	225.4	254.8	505.6	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB370C5-425AXSP04	166.90	275.5	205.3	234.2	477.5	170.5	276.8	207.8	235.7	474.5	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB550C5-625AXSP04	-	348.2	262.2	297.2	590.6	-	350.3	265.7	299.8	588.4	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB550C5-525AXSP04	202.20	331.4	248	281.8	568.8	206.8	333.2	250.9	284.2	566.3	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB550C5-425AXSP02	-	-	-	-	485.8	-	-	-	-	489.2	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.3	(2) 4"
EAW-FD15S4ZB370K8-625AXSP04	-	306.6	231.3	262	516.5	-	307.1	233.6	263.1	513	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB370K8-525AXSP04	-	290.5	217.7	247.5	495.6	-	291.2	219.9	248.5	492.2	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB370K8-425AXSP04	162.40	267.8	199.5	227.8	463.2	165.6	269	201.5	228.9	460.3	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB550K8-625AXSP04	-	335.5	253	286.5	568.3	-	337.1	255.6	288.3	564.7	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB550K8-525AXSP04	194.50	317.7	238.2	270.9	545.1	198.7	319.1	240.3	272.5	542.2	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB550K8-425AXSP04	176.90	292.8	217.9	248.8	-	180.8	294.2	220.5	250.5	-	327	17.7	4"	262	11.7	4"	392	24.9	4"
EAW-FD15S4ZB750K8-625AXSP04	-	353.1	265.7	301.2	599.1	-	354.9	268.6	303.7	596.3	490	16.5	(2) 4"	392	13.8	4"	589	23.2	(2) 4"
EAW-FD15S4ZB750K8-525AXSP04	204.50	335	250.9	285.2	575.3	209.2	337.4	253.9	287.7	573.8	406	19.1	4"	325	12.6	4"	487	22.5	(2) 4"
EAW-FD15S4ZB750K8-425AXSP02	-	-	-	-	491.6	-	-	-	-	494.4	654	10.2	(2) 4"	523	6.7	(2) 4"	785	14.3	(2) 4"
EAW-FD15S5ZB370K4-625AXSP04	248.80	392.1	298.7	336.5	653.5	252.1	392	299.7	336.8	648.2	490	20	(2) 4"	392	16.1	4"	589	28	(2) 4"
EAW-FD15S5ZB370K4-525AXSP02	-	-	-	-	588.8	-	-	-	-	588.4	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370K4-425AXSP02	-	-	-	-	545.4	-	307.6	-	-	545.9	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB550K4-625AXSP02	-	-	-	-	674	-	-	-	-	674.5	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB550K4-525AXSP02	-	-	-	-	646.4	-	-	-	-	647.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550K4-425AXSP02	-	329.8	-	-	598.1	-	336.5	-	-	598.9	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB750K4-625AXSP02	-	-	-	-	709.9	-	-	-	-	711.8	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB750K4-525AXSP02	-	380.5	-	-	682.5	-	388.1	-	-	684.2	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB750K4-425AXSP02	-	348.5	-	-	633.2	-	355.3	-	-	634.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB370K5-625AXSP04	248.80	392.1	298.7	336.5	653.5	252.1	392	299.7	336.8	648.2	490	20	(2) 4"	392	16.1	4"	589	28	(2) 4"
EAW-FD15S5ZB370K5-525AXSP02	-	-	-	-	588.8	-	-	-	-	588.4	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370K5-425AXSP02	-	-	-	-	545.4	-	307.6	-	-	545.9	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB550K5-625AXSP02	-	-	-	-	674	-	-	-	-	674.5	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB550K5-525AXSP02	-	-	-	-	646.4	-	-	-	-	647.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550K5-425AXSP02	-	329.8	-	-	598.1	-	336.5	-	-	598.9	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB750K5-625AXSP02	-	-	-	-	709.9	-	-	-	-	711.8	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB750K5-525AXSP02	-	380.5	-	-	682.5	-	388.1	-	-	684.2	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB750K5-425AXSP02	-	348.5	-	-	633.2	-	355.3	-	-	634.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB370C4-625AXSP04	252.70	398.3	303.3	341.3	664.1	256.4	399	304.9	342.7	660.2	490	20	(2) 4"	392	16.1	4"	589	28	(2) 4"
EAW-FD15S5ZB370C4-525AXSP02	-	-	-	-	602.9	-	-	-	-	604.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370C4-425AXSP02	-	310.9	-	-	562.7	-	316.7	-	-	562.4	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB550C4-625AXSP02	-	-	-	-	701	-	-	-	-	702.4	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB550C4-525AXSP02	-	-	-	-	674	-	383.4	-	-	675.4	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550C4-425AXSP02	-	344.7	-	-	625.5	-	351.2	-	-	626.3	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB370C5-625AXSP04	252.70	398.3	303.3	341.3	664.1	256.4	399	304.9	342.7	660.2	490	20	(2) 4"	392	16.1	4"	589	28	(2) 4"
EAW-FD15S5ZB370C5-525AXSP02	-	-	-	-	602.9	-	-	-	-	604.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370C5-425AXSP02	-	310.9	-	-	562.7	-	316.7	-	-	562.4	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB550C5-625AXSP02	-	-	-	-	701	-	-	-	-	702.4	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB550C5-525AXSP02	-	-	-	-	674	-	383.4	-	-	675.4	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550C5-425AXSP02	-	344.7	-	-	625.5	-	351.2	-	-	626.3	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB370K8-625AXSP04	248.80	392.1	298.7	336.5	653.5	252.1	392	299.7	336.8	648.2	490	20	(2) 4"	392	16.1	4"	589	28	(2) 4"
EAW-FD15S5ZB370K8-525AXSP02	-	-	-	-	588.8	-	-	-	-	588.4	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB370K8-425AXSP02	-	-	-	-	545.4	-	307.6	-	-	545.9	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB550K8-625AXSP02	-	-	-	-	674	-	-	-	-	674.5	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB550K8-525AXSP02	-	-	-	-	646.4	-	-	-	-	647.1	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB550K8-425AXSP02	-	329.8	-	-	598.1	-	336.5	-	-	598.9	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S5ZB750K8-625AXSP02	-	-	-	-	709.9	-	-	-	-	711.8	981	11.9	(3) 4"	785	10	(2) 4"	1177	16.7	(3) 4"
EAW-FD15S5ZB750K8-525AXSP02	-	380.5	-	-	682.5	-	388.1	-	-	684.2	818	13.4	(2) 4"	654	8.8	(2) 4"	981	15.6	(3) 4"
EAW-FD15S5ZB750K8-425AXSP02	-	348.5	-	-	633.2	-	355.3	-	-	634.2	654	11.9	(2) 4"	523	7.8	(2) 4"	785	16.7	(2) 4"
EAW-FD15S6ZB370K4-625AXSP02	-	-	-	-	750.2	-	-	-	-	747.3	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB370K4-525AXSP02	-	410.8	-	-	719.5	-	415.5	-	-	716.8	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB370K4-425AXSP02	-	376.4	-	317.6	667.2	-	380.8	-	322	665.5	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB550K4-625AXSP02	-	474.5	-	-	823.6	-	480.2	-	-	822	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB550K4-525AXSP02	-	449.7	-	379.9	790.4	-	455.2	-	386.1	788.8	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB550K4-425AXSP02	-	411.2	-	346.8	731	-	416.3	307.2	352	730.6	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB750K4-625AXSP02	-	498.8	-	-	867.9	-	505.1	-	-	866.5	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB750K4-525AXSP02	-	474.3	-	400.6	833.7	-	480.7	-	407	834.2	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB750K4-425AXSP02	-	434.5	317.1	366.1	774.4	-	440	324.5	372	774	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB370K5-625AXSP02	-	-	-	-	750.2	-	-	-	-	747.3	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB370K5-525AXSP02	-	410.8	-	-	719.5	-	415.5	-	-	716.8	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB370K5-425AXSP02	-	376.4	-	317.6	667.2	-	380.8	-	322	665.5	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB550K5-625AXSP02	-	474.5	-	-	823.6	-	480.2	-	-	822	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB550K5-525AXSP02	-	449.7	-	379.9	790.4	-	455.2	-	386.1	788.8	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB550K5-425AXSP02	-	411.2	-	346.8	731	-	416.3	307.2	352	730.6	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB750K5-625AXSP02	-	498.8	-	-	867.9	-	505.1	-	-	866.5	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB750K5-525AXSP02	-	474.3	-	400.6	833.7	-	480.7	-	407	834.2	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB750K5-425AXSP02	-	434.5	317.1	366.1	774.4	-	440	324.5	372	774	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB370C4-625AXSP02	-	-	-	-	761.3	-	-	-	-	760.9	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB370C4-525AXSP02	-	420.8	-	-	736.9	-	426.2	-	-	736.1	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB370C4-425AXSP02	-	387.7	-	326.8	687.4	-	392.3	-	332	686.8	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB550C4-625AXSP02	-	492.1	-	-	855.7	-	498.6	-	-	855	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB550C4-525AXSP02	-	468.7	-	396.1	824.4	-	474.9	-	402.2	823.5	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB550C4-425AXSP02	-	429.6	313.4	361.7	764.9	-	434.9	320.6	367.9	764.3	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB370C5-625AXSP02	-	-	-	-	761.3	-	-	-	-	760.9	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB370C5-525AXSP02	-	420.8	-	-	736.9	-	426.2	-	-	736.1	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB370C5-425AXSP02	-	387.7	-	326.8	687.4	-	392.3	-	332	686.8	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB550C5-625AXSP02	-	492.1	-	-	855.7	-	498.6	-	-	855	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB550C5-525AXSP02	-	468.7	-	396.1	824.4	-	474.9	-	402.2	823.5	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB550C5-425AXSP02	-	429.6	313.4	361.7	764.9	-	434.9	320.6	367.9	764.3	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S6ZB370K8-625AXSP02	-	-	-	-	750.2	-	-	-	-	747.3	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB370K8-525AXSP02	-	410.8	-	-	719.5	-	415.5	-	-	716.8	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB370K8-425AXSP02	-	376.4	-	317.6	667.2	-	380.8	-	322	665.5	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB550K8-625AXSP02	-	474.5	-	-	823.6	-	480.2	-	-	822	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB550K8-525AXSP02	-	449.7	-	379.9	790.4	-	455.2	-	386.1	788.8	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB550K8-425AXSP02	-	411.2	-	346.8	731	-	416.3	307.2	352	730.6	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S6ZB750K8-625AXSP02	-	498.8	-	-	867.9	-	505.1	-	-	866.5	981	13.6	(3) 4"	785	11.1	(2) 4"	1177	19.1	(3) 4"
EAW-FD15S6ZB750K8-525AXSP02	-	474.3	-	400.6	833.7	-	480.7	-	407	834.2	818	15.1	(2) 4"	654	9.9	(2) 4"	981	18	(3) 4"
EAW-FD15S6ZB750K8-425AXSP02	-	434.5	317.1	366.1	774.4	-	440	324.5	372	774	654	13.6	(2) 4"	523	9	(2) 4"	785	19.1	(2) 4"
EAW-FD15S1ZK370K4-625AXSP16	-	83.3	63.3	71.4	139.3	-	83.3	63.6	71.5	138	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK370K4-525AXSP16	48.20	77.6	58.5	66.3	131.5	48.9	77.6	58.8	66.4	130.4	97	24.2	2"	78	16	2"	116	34	2"
EAW-FD15S1ZK370K4-425AXSP12	-	70.6	52.2	59.7	123.1	-	70.9	52.9	60.2	122.3	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK550K4-625AXSP16	57.70	91.8	69.7	78.6	154.1	58.6	91.8	70	78.8	152.9	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK550K4-525AXSP16	-	83.5	62	70.9	144.3	-	84	62.9	71.5	143.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK550K4-425AXSP12	-	77.4	57.3	65.6	135.7	-	78	58.1	66.2	135.1	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK750K4-625AXSP12	-	94.1	-	80.2	161	-	95	-	81	160.6	164	17.3	3"	131	11.4	3"	196	24.3	3"
EAW-FD15S1ZK750K4-525AXSP12	-	88.4	65.7	75	153.3	-	89.2	66.7	75.8	152.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK750K4-425AXSP12	-	82.3	60.7	69.6	144.2	-	82.9	61.6	70.3	143.8	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK370K5-625AXSP16	-	83.3	63.3	71.4	139.3	-	83.3	63.6	71.5	138	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK370K5-525AXSP16	48.20	77.6	58.5	66.3	131.5	48.9	77.6	58.8	66.4	130.4	97	24.2	2"	78	16	2"	116	34	2"
EAW-FD15S1ZK370K5-425AXSP12	-	70.6	52.2	59.7	123.1	-	70.9	52.9	60.2	122.3	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK550K5-625AXSP16	57.70	91.8	69.7	78.6	154.1	58.6	91.8	70	78.8	152.9	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK550K5-525AXSP12	-	83.5	62	70.9	144.3	-	84	62.9	71.5	143.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK550K5-425AXSP12	-	77.4	57.3	65.6	135.7	-	78	58.1	66.2	135.1	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK750K5-625AXSP12	-	94.1	-	80.2	161	-	95	-	81	160.6	164	17.3	3"	131	11.4	3"	196	24.3	3"
EAW-FD15S1ZK750K5-525AXSP12	-	88.4	65.7	75	153.3	-	89.2	66.7	75.8	152.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK750K5-425AXSP12	-	82.3	60.7	69.6	144.2	-	82.9	61.6	70.3	143.8	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK370C4-625AXSP16	-	85.5	64.9	73.3	143	-	85.6	65.3	73.4	142	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK370C4-525AXSP12	-	78.2	-	66.5	135	-	78.7	-	67.1	134.3	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK370C4-425AXSP12	-	72.9	53.9	61.8	127.4	-	73.3	54.7	62.4	126.8	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK550C4-625AXSP16	60.20	96	72.7	82.1	161.1	61.2	96.1	73.1	82.3	160.2	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK550C4-525AXSP12	-	87.3	64.9	74.1	151.3	-	88	65.9	74.8	150.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK550C4-425AXSP12	-	81	59.9	68.6	142.1	-	81.7	60.7	69.2	141.6	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK750C4-525AXSP12	-	90.9	67.4	77.1	157.8	-	91.7	68.6	78	157.4	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK750C4-425AXSP12	-	84.6	62.5	71.7	148.7	51.6	85.5	63.5	72.5	148.4	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK370C5-625AXSP16	-	85.5	64.9	73.3	143	-	85.6	65.3	73.4	142	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK370C5-525AXSP12	-	78.2	-	66.5	135	-	78.7	-	67.1	134.3	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK370C5-425AXSP12	-	72.9	53.9	61.8	127.4	-	73.3	54.7	62.4	126.8	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK550C5-625AXSP16	60.20	96	72.7	82.1	161.1	61.2	96.1	73.1	82.3	160.2	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK550C5-525AXSP12	-	87.3	64.9	74.1	151.3	-	88	65.9	74.8	150.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK550C5-425AXSP12	-	81	59.9	68.6	142.1	-	81.7	60.7	69.2	141.6	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK750C5-525AXSP12	-	90.9	67.4	77.1	157.8	-	91.7	68.6	78	157.4	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK750C5-425AXSP12	-	84.6	62.5	71.7	148.7	51.6	85.5	63.5	72.5	148.4	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK370K8-625AXSP16	-	83.3	63.3	71.4	139.3	-	83.3	63.6	71.5	138	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK370K8-525AXSP16	48.20	77.6	58.5	66.3	131.5	48.9	77.6	58.8	66.4	130.4	97	24.2	2"	78	16	2"	116	34	2"
EAW-FD15S1ZK370K8-425AXSP12	-	70.6	52.2	59.7	123.1	-	70.9	52.9	60.2	122.3	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK550K8-625AXSP16	57.70	91.8	69.7	78.6	154.1	58.6	91.8	70	78.8	152.9	121	21.5	3"	97	17.3	2"	145	30.1	3"
EAW-FD15S1ZK550K8-525AXSP12	-	83.5	62	70.9	144.3	-	84	62.9	71.5	143.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK550K8-425AXSP12	-	77.4	57.3	65.6	135.7	-	78	58.1	66.2	135.1	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S1ZK750K8-625AXSP12	-	94.1	-	80.2	161	-	95	-	81	160.6	164	17.3	3"	131	11.4	3"	196	24.3	3"
EAW-FD15S1ZK750K8-525AXSP12	-	88.4	65.7	75	153.3	-	89.2	66.7	75.8	152.8	133	16.6	3"	107	14.8	2"	160	23.3	3"
EAW-FD15S1ZK750K8-425AXSP12	-	82.3	60.7	69.6	144.2	-	82.9	61.6	70.3	143.8	109	20.1	2"	87	13.2	2"	131	22.7	3"
EAW-FD15S2ZK370K4-625AXSP08	-	166.2	126.1	142.3	278	-	165.9	126.7	142.4	275.3	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK370K4-525AXSP08	97.60	157	118.4	134.3	266.1	99	157.2	119.2	134.3	263.6	200	20.9	3"	160	13.8	3"	240	29.4	3"
EAW-FD15S2ZK370K4-425AXSP06	-	140.2	103.6	118.8	244.7	-	141.1	105.1	119.6	243.1	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK550K4-625AXSP08	114.80	182.9	138.7	156.7	307.1	116.6	183.1	139.4	156.9	304.6	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK550K4-525AXSP06	-	168	-	142.5	290.5	-	169	126.7	143.9	289.1	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK550K4-425AXSP06	-	153.8	113.6	130.1	269.6	-	154.9	115.4	131.6	268.4	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK750K4-625AXSP08	121.20	193.6	146.6	165.5	325.7	123.3	194.1	147.7	166.3	323.9	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK750K4-525AXSP06	-	178	132.1	151	308.8	-	179.4	134.1	152.5	307.7	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK750K4-425AXSP06	-	163.3	120.4	138.1	286.5	-	164.6	122.4	139.6	285.8	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK370K5-625AXSP08	-	166.2	126.1	142.3	278	-	165.9	126.7	142.4	275.3	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK370K5-525AXSP08	97.60	157	118.4	134.3	266.1	99	157.2	119.2	134.3	263.6	200	20.9	3"	160	13.8	3"	240	29.4	3"
EAW-FD15S2ZK370K5-425AXSP06	-	140.2	103.6	118.8	244.7	-	141.1	105.1	119.6	243.1	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK550K5-625AXSP08	114.80	182.9	138.7	156.7	307.1	116.6	183.1	139.4	156.9	304.6	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK550K5-525AXSP06	-	168	-	142.5	290.5	-	169	126.7	143.9	289.1	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK550K5-425AXSP06	-	153.8	113.6	130.1	269.6	-	154.9	115.4	131.6	268.4	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK750K5-625AXSP08	121.20	193.6	146.6	165.5	325.7	123.3	194.1	147.7	166.3	323.9	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK750K5-525AXSP06	-	178	132.1	151	308.8	-	179.4	134.1	152.5	307.7	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK750K5-425AXSP06	-	163.3	120.4	138.1	286.5	-	164.6	122.4	139.6	285.8	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK370C4-625AXSP08	-	170.3	129.3	145.9	285	-	170.4	130	146.2	283	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK370C4-525AXSP08	100.50	162	122	138.2	274.4	102.2	162.1	122.8	138.7	272.6	200	20.9	3"	160	13.8	3"	240	29.4	3"
EAW-FD15S2ZK370C4-425AXSP06	-	144.8	107.1	122.6	253.3	-	145.9	108.7	123.8	252	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK550C4-625AXSP08	119.80	191.2	144.8	163.4	321.4	121.7	191.6	145.9	164.2	319.6	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK550C4-525AXSP06	-	175.8	130.5	149.2	304.7	-	177.2	132.5	150.7	303.6	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK550C4-425AXSP06	-	160.9	118.8	136.3	282.5	-	162.2	120.6	137.7	281.5	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK750C4-525AXSP06	-	183	135.8	155.1	317.4	-	184.6	138	157	316.9	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK750C4-425AXSP06	-	168.3	124	142.3	295.9	102.3	169.8	126.1	143.8	294.9	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK370C5-625AXSP08	-	170.3	129.3	145.9	285	-	170.4	130	146.2	283	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK370C5-525AXSP08	100.50	162	122	138.2	274.4	102.2	162.1	122.8	138.7	272.6	200	20.9	3"	160	13.8	3"	240	29.4	3"
EAW-FD15S2ZK370C5-425AXSP06	-	144.8	107.1	122.6	253.3	-	145.9	108.7	123.8	252	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK550C5-625AXSP08	119.80	191.2	144.8	163.4	321.4	121.7	191.6	145.9	164.2	319.6	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK550C5-525AXSP06	-	175.8	130.5	149.2	304.7	-	177.2	132.5	150.7	303.6	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK550C5-425AXSP06	-	160.9	118.8	136.3	282.5	-	162.2	120.6	137.7	281.5	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK750C5-525AXSP06	-	183	135.8	155.1	317.4	-	184.6	138	157	316.9	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK750C5-425AXSP06	-	168.3	124	142.3	295.9	102.3	169.8	126.1	143.8	294.9	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK370K8-625AXSP08	-	166.2	126.1	142.3	278	-	165.9	126.7	142.4	275.3	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK370K8-525AXSP08	97.60	157	118.4	134.3	266.1	99	157.2	119.2	134.3	263.6	200	20.9	3"	160	13.8	3"	240	29.4	3"
EAW-FD15S2ZK370K8-425AXSP06	-	140.2	103.6	118.8	244.7	-	141.1	105.1	119.6	243.1	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK550K8-625AXSP08	114.80	182.9	138.7	156.7	307.1	116.6	183.1	139.4	156.9	304.6	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK550K8-525AXSP06	-	168	-	142.5	290.5	-	169	126.7	143.9	289.1	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK550K8-425AXSP06	-	153.8	113.6	130.1	269.6	-	154.9	115.4	131.6	268.4	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S2ZK750K8-625AXSP08	121.20	193.6	146.6	165.5	325.7	123.3	194.1	147.7	166.3	323.9	242	22.3	3"	194	14.7	3"	291	27	4"
EAW-FD15S2ZK750K8-525AXSP06	-	178	132.1	151	308.8	-	179.4	134.1	152.5	307.7	272	15.2	4"	218	12.5	3"	327	21.3	4"
EAW-FD15S2ZK750K8-425AXSP06	-	163.3	120.4	138.1	286.5	-	164.6	122.4	139.6	285.8	218	17	3"	174	11.2	3"	262	20.4	4"
EAW-FD15S3ZK370K4-625AXSP06	161.00	252.9	192.8	217	420.5	162.7	252.1	193.3	216.8	416.4	327	21.8	4"	262	14.4	4"	392	30.6	4"
EAW-FD15S3ZK370K4-525AXSP04	-	226.9	-	192.6	391.8	-	228.3	-	194.4	389.2	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK370K4-425AXSP04	-	208.8	154.3	176.9	364.8	-	210.2	156.5	178.4	363.1	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK550K4-625AXSP04	-	263.9	-	-	452.2	-	265.9	-	-	449.7	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK550K4-525AXSP04	-	249.2	-	211.6	432.2	-	251.2	187.8	213.8	430.1	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK550K4-425AXSP04	-	229.4	169.2	194.1	401.9	-	231.1	171.8	196	400.2	327	15.4	4"	262	10.1	4"	392	21.6	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S3ZK750K4-625AXSP04	-	279.2	-	237.6	478.8	-	281.7	-	240.1	477.5	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK750K4-525AXSP04	-	264.4	195.9	224.1	458.6	-	266.2	199.1	226.5	457.1	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK750K4-425AXSP04	-	243.1	179.3	205.7	427.7	-	245.1	182.2	208.2	426	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK370K5-625AXSP06	161.00	252.9	192.8	217	420.5	162.7	252.1	193.3	216.8	416.4	327	21.8	4"	262	14.4	4"	392	30.6	4"
EAW-FD15S3ZK370K5-525AXSP04	-	226.9	-	192.6	391.8	-	228.3	-	194.4	389.2	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK370K5-425AXSP04	-	208.8	154.3	176.9	364.8	-	210.2	156.5	178.4	363.1	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK550K5-625AXSP04	-	263.9	-	-	452.2	-	265.9	-	-	449.7	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK550K5-525AXSP04	-	249.2	-	211.6	432.2	-	251.2	187.8	213.8	430.1	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK550K5-425AXSP04	-	229.4	169.2	194.1	401.9	-	231.1	171.8	196	400.2	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK750K5-625AXSP04	-	279.2	-	237.6	478.8	-	281.7	-	240.1	477.5	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK750K5-525AXSP04	-	264.4	195.9	224.1	458.6	-	266.2	199.1	226.5	457.1	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK750K5-425AXSP04	-	243.1	179.3	205.7	427.7	-	245.1	182.2	208.2	426	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK370C4-625AXSP06	165.00	259.2	197.6	222.5	431.1	167	259	198.4	222.6	428.1	327	21.8	4"	262	14.4	4"	392	30.6	4"
EAW-FD15S3ZK370C4-525AXSP04	-	233.6	-	198.4	403.9	-	235.4	-	200.3	401.9	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK370C4-425AXSP04	-	215.6	159.5	182.8	377.6	-	217.4	161.8	184.4	375.7	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK550C4-625AXSP04	-	275.7	-	234.6	472.6	-	278.1	-	237.1	471.1	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK550C4-525AXSP04	-	261.1	193.6	221.4	453.3	-	263.3	196.7	223.7	451.7	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK550C4-425AXSP04	-	239.9	176.8	203	421.6	-	241.6	179.6	204.9	419.5	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK750C4-525AXSP04	-	271.3	201.1	230.2	472.1	-	274.2	204.8	233.1	471.4	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK750C4-425AXSP04	-	250.5	184.6	211.7	440.9	152.3	252.8	187.8	214.4	439.5	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK370C5-625AXSP06	165.00	259.2	197.6	222.5	431.1	167	259	198.4	222.6	428.1	327	21.8	4"	262	14.4	4"	392	30.6	4"
EAW-FD15S3ZK370C5-525AXSP04	-	233.6	-	198.4	403.9	-	235.4	-	200.3	401.9	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK370C5-425AXSP04	-	215.6	159.5	182.8	377.6	-	217.4	161.8	184.4	375.7	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK550C5-625AXSP04	-	275.7	-	234.6	472.6	-	278.1	-	237.1	471.1	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK550C5-525AXSP04	-	261.1	193.6	221.4	453.3	-	263.3	196.7	223.7	451.7	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK550C5-425AXSP04	-	239.9	176.8	203	421.6	-	241.6	179.6	204.9	419.5	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK750C5-525AXSP04	-	271.3	201.1	230.2	472.1	-	274.2	204.8	233.1	471.4	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK750C5-425AXSP04	-	250.5	184.6	211.7	440.9	152.3	252.8	187.8	214.4	439.5	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK370K8-625AXSP06	161.00	252.9	192.8	217	420.5	162.7	252.1	193.3	216.8	416.4	327	21.8	4"	262	14.4	4"	392	30.6	4"
EAW-FD15S3ZK370K8-525AXSP04	-	226.9	-	192.6	391.8	-	228.3	-	194.4	389.2	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK370K8-425AXSP04	-	208.8	154.3	176.9	364.8	-	210.2	156.5	178.4	363.1	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK550K8-625AXSP04	-	263.9	-	-	452.2	-	265.9	-	-	449.7	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK550K8-525AXSP04	-	249.2	-	211.6	432.2	-	251.2	187.8	213.8	430.1	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK550K8-425AXSP04	-	229.4	169.2	194.1	401.9	-	231.1	171.8	196	400.2	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S3ZK750K8-625AXSP04	-	279.2	-	237.6	478.8	-	281.7	-	240.1	477.5	490	14.2	(2) 4"	392	12.3	4"	589	20	(2) 4"
EAW-FD15S3ZK750K8-525AXSP04	-	264.4	195.9	224.1	458.6	-	266.2	199.1	226.5	457.1	406	16.8	4"	325	11.1	4"	487	19.3	(2) 4"
EAW-FD15S3ZK750K8-425AXSP04	-	243.1	179.3	205.7	427.7	-	245.1	182.2	208.2	426	327	15.4	4"	262	10.1	4"	392	21.6	4"
EAW-FD15S4ZK370K4-625AXSP04	-	331.6	251.9	284.1	555.3	-	331.4	253	284.4	550	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK370K4-525AXSP04	194.90	314.1	236.9	268.1	532.2	198.1	313.9	238	268.7	527.9	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK370K4-425AXSP04	177.50	289.1	216.7	246.5	496.1	180	289.3	217.9	247.1	492.1	327	19.2	4"	262	12.7	4"	392	27	4"
EAW-FD15S4ZK550K4-625AXSP04	229.00	365.3	276.6	312.5	613.5	232.5	365.3	278.4	313.3	609.3	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK550K4-525AXSP04	213.70	345.4	259.8	294.6	587.5	217	345.8	261.7	295.4	582.8	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK550K4-425AXSP02	-	-	-	-	505.2	-	-	-	-	506.1	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750K4-625AXSP04	241.70	386.2	292.2	330.4	650.6	245.8	387.2	294.6	331.7	647	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK750K4-525AXSP02	-	-	-	-	580.3	-	-	-	-	581.3	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK750K4-425AXSP02	-	-	-	-	535.8	-	-	-	-	538	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370K5-625AXSP04	-	331.6	251.9	284.1	555.3	-	331.4	253	284.4	550	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK370K5-525AXSP04	194.90	314.1	236.9	268.1	532.2	198.1	313.9	238	268.7	527.9	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK370K5-425AXSP04	177.50	289.1	216.7	246.5	496.1	180	289.3	217.9	247.1	492.1	327	19.2	4"	262	12.7	4"	392	27	4"
EAW-FD15S4ZK550K5-625AXSP04	229.00	365.3	276.6	312.5	613.5	232.5	365.3	278.4	313.3	609.3	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK550K5-525AXSP04	213.70	345.4	259.8	294.6	587.5	217	345.8	261.7	295.4	582.8	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK550K5-425AXSP02	-	-	-	-	505.2	-	-	-	-	506.1	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750K5-625AXSP04	241.70	386.2	292.2	330.4	650.6	245.8	387.2	294.6	331.7	647	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK750K5-525AXSP02	-	-	-	-	580.3	-	-	-	-	581.3	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK750K5-425AXSP02	-	-	-	-	535.8	-	-	-	-	538	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370C4-625AXSP04	-	340.1	257.8	290.9	569.3	-	340.4	259.7	292	565.4	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK370C4-525AXSP04	200.70	323.5	244	276.3	548.8	204	323.8	245.7	277	545.2	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK370C4-425AXSP02	-	-	-	-	474.7	-	-	-	-	475	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK550C4-625AXSP04	238.80	381.3	288.7	326.3	642.1	242.7	382.2	290.9	327.5	638.3	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK550C4-525AXSP02	-	-	-	-	572.9	-	-	-	-	574.6	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK550C4-425AXSP02	-	-	-	-	528.5	-	-	-	-	530	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750C4-525AXSP02	-	-	-	-	597	-	-	-	-	599.3	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK750C4-425AXSP02	-	-	-	-	552.8	-	307.4	-	-	554.6	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370C5-625AXSP04	-	340.1	257.8	290.9	569.3	-	340.4	259.7	292	565.4	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK370C5-525AXSP04	200.70	323.5	244	276.3	548.8	204	323.8	245.7	277	545.2	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK370C5-425AXSP02	-	-	-	-	474.7	-	-	-	-	475	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK550C5-625AXSP04	238.80	381.3	288.7	326.3	642.1	242.7	382.2	290.9	327.5	638.3	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK550C5-525AXSP02	-	-	-	-	572.9	-	-	-	-	574.6	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK550C5-425AXSP02	-	-	-	-	528.5	-	-	-	-	530	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750C5-525AXSP02	-	-	-	-	597	-	-	-	-	599.3	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK750C5-425AXSP02	-	-	-	-	552.8	-	307.4	-	-	554.6	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK370K8-625AXSP04	-	331.6	251.9	284.1	555.3	-	331.4	253	284.4	550	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK370K8-525AXSP04	194.90	314.1	236.9	268.1	532.2	198.1	313.9	238	268.7	527.9	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK370K8-425AXSP04	177.50	289.1	216.7	246.5	496.1	180	289.3	217.9	247.1	492.1	327	19.2	4"	262	12.7	4"	392	27	4"
EAW-FD15S4ZK550K8-625AXSP04	229.00	365.3	276.6	312.5	613.5	232.5	365.3	278.4	313.3	609.3	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK550K8-525AXSP04	213.70	345.4	259.8	294.6	587.5	217	345.8	261.7	295.4	582.8	406	20.7	4"	325	13.6	4"	487	24.6	(2) 4"
EAW-FD15S4ZK550K8-425AXSP02	-	-	-	-	505.2	-	-	-	-	506.1	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S4ZK750K8-625AXSP04	241.70	386.2	292.2	330.4	650.6	245.8	387.2	294.6	331.7	647	490	18	(2) 4"	392	14.8	4"	589	25.3	(2) 4"
EAW-FD15S4ZK750K8-525AXSP02	-	-	-	-	580.3	-	-	-	-	581.3	818	12.4	(2) 4"	654	8.1	(2) 4"	981	14.2	(3) 4"
EAW-FD15S4ZK750K8-425AXSP02	-	-	-	-	535.8	-	-	-	-	538	654	10.9	(2) 4"	523	7.2	(2) 4"	785	15.4	(2) 4"
EAW-FD15S5ZK370K4-625AXSP02	-	-	-	-	663.3	-	-	-	-	660.6	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370K4-525AXSP02	-	-	-	-	635.5	-	-	-	-	633.2	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK370K4-425AXSP02	-	329.6	-	-	587.6	-	334.1	-	-	586.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550K4-625AXSP02	-	-	-	-	732	-	-	-	-	730.1	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550K4-525AXSP02	-	396.2	-	-	700.4	-	401.3	-	-	699.2	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK550K4-425AXSP02	-	362	-	304.4	647.5	-	366.7	-	309.6	646.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750K4-625AXSP02	-	-	-	-	775.6	-	-	-	-	774.8	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK750K4-525AXSP02	-	419.9	-	-	743.7	-	426.2	-	-	742.6	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK750K4-425AXSP02	-	383.8	-	322.3	687.2	-	389.7	-	328.7	687.3	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370K5-625AXSP02	-	-	-	-	663.3	-	-	-	-	660.6	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370K5-525AXSP02	-	-	-	-	635.5	-	-	-	-	633.2	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK370K5-425AXSP02	-	329.6	-	-	587.6	-	334.1	-	-	586.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550K5-625AXSP02	-	-	-	-	732	-	-	-	-	730.1	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550K5-525AXSP02	-	396.2	-	-	700.4	-	401.3	-	-	699.2	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK550K5-425AXSP02	-	362	-	304.4	647.5	-	366.7	-	309.6	646.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750K5-625AXSP02	-	-	-	-	775.6	-	-	-	-	774.8	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK750K5-525AXSP02	-	419.9	-	-	743.7	-	426.2	-	-	742.6	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK750K5-425AXSP02	-	383.8	-	322.3	687.2	-	389.7	-	328.7	687.3	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370C4-625AXSP02	-	-	-	-	679.8	-	-	-	-	678.9	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370C4-525AXSP02	-	-	-	-	655	-	-	-	-	653.7	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK370C4-425AXSP02	-	340.8	-	-	608.9	-	345.4	-	-	607.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S5ZK550C4-625AXSP02	-	-	-	-	765.6	-	-	-	-	764.5	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550C4-525AXSP02	-	414.8	-	-	734.2	-	420.9	-	-	732.9	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK550C4-425AXSP02	-	378.2	-	318.1	677.7	-	383.6	-	323.9	676.9	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750C4-525AXSP02	-	431.4	-	-	764.2	-	438.1	-	-	764.7	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK750C4-425AXSP02	-	395.3	-	332.1	709.3	-	401.7	-	338.3	709.9	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370C5-625AXSP02	-	-	-	-	679.8	-	-	-	-	678.9	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370C5-525AXSP02	-	-	-	-	655	-	-	-	-	653.7	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK370C5-425AXSP02	-	340.8	-	-	608.9	-	345.4	-	-	607.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550C5-625AXSP02	-	-	-	-	765.6	-	-	-	-	764.5	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550C5-525AXSP02	-	414.8	-	-	734.2	-	420.9	-	-	732.9	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK550C5-425AXSP02	-	378.2	-	318.1	677.7	-	383.6	-	323.9	676.9	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750C5-525AXSP02	-	431.4	-	-	764.2	-	438.1	-	-	764.7	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK750C5-425AXSP02	-	395.3	-	332.1	709.3	-	401.7	-	338.3	709.9	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK370K8-625AXSP02	-	-	-	-	663.3	-	-	-	-	660.6	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK370K8-525AXSP02	-	-	-	-	635.5	-	-	-	-	633.2	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK370K8-425AXSP02	-	329.6	-	-	587.6	-	334.1	-	-	586.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK550K8-625AXSP02	-	-	-	-	732	-	-	-	-	730.1	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK550K8-525AXSP02	-	396.2	-	-	700.4	-	401.3	-	-	699.2	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK550K8-425AXSP02	-	362	-	304.4	647.5	-	366.7	-	309.6	646.1	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S5ZK750K8-625AXSP02	-	-	-	-	775.6	-	-	-	-	774.8	981	12.8	(3) 4"	785	10.6	(2) 4"	1177	18.1	(3) 4"
EAW-FD15S5ZK750K8-525AXSP02	-	419.9	-	-	743.7	-	426.2	-	-	742.6	818	14.3	(2) 4"	654	9.4	(2) 4"	981	16.9	(3) 4"
EAW-FD15S5ZK750K8-425AXSP02	-	383.8	-	322.3	687.2	-	389.7	-	328.7	687.3	654	12.8	(2) 4"	523	8.4	(2) 4"	785	18.1	(2) 4"
EAW-FD15S6ZK370K4-625AXSP02	-	471.7	-	-	808	-	475.2	-	-	802.5	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK370K4-525AXSP02	-	446.9	-	379.4	774.1	-	450.4	-	383.3	770.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK370K4-425AXSP02	-	409.5	-	346.4	717.4	-	411.7	306.3	349.7	714.2	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK550K4-625AXSP02	-	518.9	-	-	891.9	-	523	-	-	887.2	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK550K4-525AXSP02	-	491.3	-	416.7	853.7	-	495.5	-	421.2	850.8	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK550K4-425AXSP02	-	448.7	330.5	379.5	789.7	-	453.2	336	383.7	786.6	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK750K4-625AXSP02	-	548.7	-	466.3	945.4	-	554	-	472.4	942.9	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK750K4-525AXSP02	-	520.2	385.4	441.2	906.8	-	524.9	391.7	446.1	903.9	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK750K4-425AXSP02	-	476.1	350.1	402.3	840	-	480.3	356.5	407.1	837	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK370K5-625AXSP02	-	471.7	-	-	808	-	475.2	-	-	802.5	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK370K5-525AXSP02	-	446.9	-	379.4	774.1	-	450.4	-	383.3	770.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK370K5-425AXSP02	-	409.5	-	346.4	717.4	-	411.7	306.3	349.7	714.2	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK550K5-625AXSP02	-	518.9	-	-	891.9	-	523	-	-	887.2	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK550K5-525AXSP02	-	491.3	-	416.7	853.7	-	495.5	-	421.2	850.8	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK550K5-425AXSP02	-	448.7	330.5	379.5	789.7	-	453.2	336	383.7	786.6	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK750K5-625AXSP02	-	548.7	-	466.3	945.4	-	554	-	472.4	942.9	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK750K5-525AXSP02	-	520.2	385.4	441.2	906.8	-	524.9	391.7	446.1	903.9	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK750K5-425AXSP02	-	476.1	350.1	402.3	840	-	480.3	356.5	407.1	837	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK370C4-625AXSP02	-	483.7	-	-	828.2	-	488	-	-	824.7	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK370C4-525AXSP02	-	460.7	-	390.8	799.1	-	464.5	-	394.9	795.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK370C4-425AXSP02	-	422.8	311.5	357.9	742.4	-	426.5	316.5	361.2	738.8	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK550C4-625AXSP02	-	541.9	-	460.6	933.1	-	546.8	-	466.4	930.4	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK550C4-525AXSP02	-	513.8	380.2	436	895.1	-	519.1	387.1	440.7	892.1	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK550C4-425AXSP02	-	470	345.6	396.9	828.2	-	473.5	351.4	401.8	824.4	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK750C4-525AXSP02	-	534.6	395.4	453.1	932	-	540.6	402.9	459.1	930.9	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK750C4-425AXSP02	-	490.5	360.6	414.3	865.7	-	495.2	366.8	419.7	864.8	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK370C5-625AXSP02	-	483.7	-	-	828.2	-	488	-	-	824.7	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK370C5-525AXSP02	-	460.7	-	390.8	799.1	-	464.5	-	394.9	795.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK370C5-425AXSP02	-	422.8	311.5	357.9	742.4	-	426.5	316.5	361.2	738.8	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK550C5-625AXSP02	-	541.9	-	460.6	933.1	-	546.8	-	466.4	930.4	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK550C5-525AXSP02	-	513.8	380.2	436	895.1	-	519.1	387.1	440.7	892.1	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK550C5-425AXSP02	-	470	345.6	396.9	828.2	-	473.5	351.4	401.8	824.4	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK750C5-525AXSP02	-	534.6	395.4	453.1	932	-	540.6	402.9	459.1	930.9	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK750C5-425AXSP02	-	490.5	360.6	414.3	865.7	-	495.2	366.8	419.7	864.8	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK370K8-625AXSP02	-	471.7	-	-	808	-	475.2	-	-	802.5	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK370K8-525AXSP02	-	446.9	-	379.4	774.1	-	450.4	-	383.3	770.2	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK370K8-425AXSP02	-	409.5	-	346.4	717.4	-	411.7	306.3	349.7	714.2	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK550K8-625AXSP02	-	518.9	-	-	891.9	-	523	-	-	887.2	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK550K8-525AXSP02	-	491.3	-	416.7	853.7	-	495.5	-	421.2	850.8	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK550K8-425AXSP02	-	448.7	330.5	379.5	789.7	-	453.2	336	383.7	786.6	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S6ZK750K8-625AXSP02	-	548.7	-	466.3	945.4	-	554	-	472.4	942.9	981	14.8	(3) 4"	785	11.9	(2) 4"	1177	20.8	(3) 4"
EAW-FD15S6ZK750K8-525AXSP02	-	520.2	385.4	441.2	906.8	-	524.9	391.7	446.1	903.9	818	16.3	(2) 4"	654	10.7	(2) 4"	981	19.6	(3) 4"
EAW-FD15S6ZK750K8-425AXSP02	-	476.1	350.1	402.3	840	-	480.3	356.5	407.1	837	654	14.8	(2) 4"	523	9.7	(2) 4"	785	20.8	(2) 4"
EAW-FD15S1PB370K4-625AXSP16	-	71.5	54.1	61.2	120.6	-	71.8	54.5	61.5	119.8	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB370K4-525AXSP16	-	68.3	51.3	58.2	116.6	42.8	68.6	51.8	58.5	115.8	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB370K4-425AXSP12	-	60.3	-	50.9	106.3	-	60.9	45.1	51.6	106.1	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB550K4-625AXSP16	-	78	58.8	66.6	131.9	-	78.3	59.4	67	131.2	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB550K4-525AXSP16	45.60	74.5	55.8	63.4	127.3	46.6	74.8	56.4	63.8	126.9	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB550K4-425AXSP12	-	65.6	48.1	55.4	116.1	-	66.4	49.1	56.2	115.9	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB750K4-625AXSP16	50.50	81.7	61.5	69.7	138.4	51.7	82.1	62.2	70.2	137.9	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB750K4-525AXSP12	-	74.7	-	63.2	130.7	-	75.7	56.3	64.2	130.7	121	15.2	3"	97	13.1	2"	145	21.3	3"
EAW-FD15S1PB750K4-425AXSP12	-	69	50.5	58.2	122.4	-	69.8	51.6	59.1	122.4	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB370K5-625AXSP16	-	71.5	54.1	61.2	120.6	-	71.8	54.5	61.5	119.8	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB370K5-525AXSP16	-	68.3	51.3	58.2	116.6	42.8	68.6	51.8	58.5	115.8	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB370K5-425AXSP12	-	60.3	-	50.9	106.3	-	60.9	45.1	51.6	106.1	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB550K5-625AXSP16	-	78	58.8	66.6	131.9	-	78.3	59.4	67	131.2	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB550K5-525AXSP16	45.60	74.5	55.8	63.4	127.3	46.6	74.8	56.4	63.8	126.9	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB550K5-425AXSP12	-	65.6	48.1	55.4	116.1	-	66.4	49.1	56.2	115.9	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB750K5-625AXSP16	50.50	81.7	61.5	69.7	138.4	51.7	82.1	62.2	70.2	137.9	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB750K5-525AXSP12	-	74.7	-	63.2	130.7	-	75.7	56.3	64.2	130.7	121	15.2	3"	97	13.1	2"	145	21.3	3"
EAW-FD15S1PB750K5-425AXSP12	-	69	50.5	58.2	122.4	-	69.8	51.6	59.1	122.4	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB370C4-625AXSP16	-	71.7	54.2	61.3	120.9	-	72.2	54.8	61.8	120.5	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB370C4-525AXSP16	42.50	69.2	52	59	118.1	43.5	69.7	52.6	59.4	117.7	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB370C4-425AXSP12	-	61.7	45.2	52	108.8	-	62.4	46.2	52.8	108.8	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB550C4-525AXSP12	-	73.7	-	62.4	129.1	-	74.8	-	63.4	129.2	121	15.2	3"	97	13.1	2"	145	21.3	3"
EAW-FD15S1PB550C4-425AXSP12	-	68.2	50	57.5	120.9	-	69.2	51.1	58.5	120.9	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB370C5-625AXSP16	-	71.7	54.2	61.3	120.9	-	72.2	54.8	61.8	120.5	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB370C5-525AXSP16	42.50	69.2	52	59	118.1	43.5	69.7	52.6	59.4	117.7	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB370C5-425AXSP12	-	61.7	45.2	52	108.8	-	62.4	46.2	52.8	108.8	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB550C5-525AXSP12	-	73.7	-	62.4	129.1	-	74.8	-	63.4	129.2	121	15.2	3"	97	13.1	2"	145	21.3	3"
EAW-FD15S1PB550C5-425AXSP12	-	68.2	50	57.5	120.9	-	69.2	51.1	58.5	120.9	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB370K8-625AXSP16	-	71.5	54.1	61.2	120.6	-	71.8	54.5	61.5	119.8	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB370K8-525AXSP16	-	68.3	51.3	58.2	116.6	42.8	68.6	51.8	58.5	115.8	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB370K8-425AXSP12	-	60.3	-	50.9	106.3	-	60.9	45.1	51.6	106.1	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB550K8-625AXSP16	-	78	58.8	66.6	131.9	-	78.3	59.4	67	131.2	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB550K8-525AXSP16	45.60	74.5	55.8	63.4	127.3	46.6	74.8	56.4	63.8	126.9	91	22.1	2"	73	14.6	2"	109	31.1	2"
EAW-FD15S1PB550K8-425AXSP12	-	65.6	48.1	55.4	116.1	-	66.4	49.1	56.2	115.9	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S1PB750K8-625AXSP16	50.50	81.7	61.5	69.7	138.4	51.7	82.1	62.2	70.2	137.9	109	23.5	2"	87	15.5	2"	131	27.6	3"
EAW-FD15S1PB750K8-525AXSP12	-	74.7	-	63.2	130.7	-	75.7	56.3	64.2	130.7	121	15.2	3"	97	13.1	2"	145	21.3	3"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S1PB750K8-425AXSP12	-	69	50.5	58.2	122.4	-	69.8	51.6	59.1	122.4	97	17.8	2"	78	11.8	2"	116	25.1	2"
EAW-FD15S2PB370K4-625AXSP08	-	142.6	107.7	121.8	240.3	-	143	108.7	122.5	239	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB370K4-525AXSP08	-	136	102.1	115.9	232.2	85.2	136.6	103.1	116.5	231	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB370K4-425AXSP06	-	119.7	-	101	211.2	-	121	-	102.3	210.9	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB550K4-625AXSP08	-	155.3	117.1	132.6	262.9	-	156	118.4	133.6	261.8	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB550K4-525AXSP08	90.70	148.2	110.9	126.2	254	92.7	148.9	112.3	127.2	252.7	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB550K4-425AXSP06	-	130.1	95.4	109.8	230.7	-	131.9	97.4	111.5	230.4	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB750K4-625AXSP08	-	162.7	122.6	138.7	275.7	102.9	163.7	123.8	139.8	274.7	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB750K4-525AXSP06	-	148.4	-	125.5	260.3	-	150.5	-	127.5	260.3	242	16.7	3"	194	10.9	3"	291	19.1	4"
EAW-FD15S2PB750K4-425AXSP06	-	136.9	100.2	115.5	243.2	-	138.9	102.5	117.4	243.1	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB370K5-625AXSP08	-	142.6	107.7	121.8	240.3	-	143	108.7	122.5	239	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB370K5-525AXSP08	-	136	102.1	115.9	232.2	85.2	136.6	103.1	116.5	231	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB370K5-425AXSP06	-	119.7	-	101	211.2	-	121	-	102.3	210.9	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB550K5-625AXSP08	-	155.3	117.1	132.6	262.9	-	156	118.4	133.6	261.8	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB550K5-525AXSP08	90.70	148.2	110.9	126.2	254	92.7	148.9	112.3	127.2	252.7	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB550K5-425AXSP06	-	130.1	95.4	109.8	230.7	-	131.9	97.4	111.5	230.4	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB750K5-625AXSP08	-	162.7	122.6	138.7	275.7	102.9	163.7	123.8	139.8	274.7	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB750K5-525AXSP06	-	148.4	-	125.5	260.3	-	150.5	-	127.5	260.3	242	16.7	3"	194	10.9	3"	291	19.1	4"
EAW-FD15S2PB750K5-425AXSP06	-	136.9	100.2	115.5	243.2	-	138.9	102.5	117.4	243.1	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB370C4-625AXSP08	-	142.9	107.9	122.1	240.8	-	143.9	109.2	123.2	240.2	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB370C4-525AXSP08	84.60	137.7	103.4	117.5	235.6	86.5	138.7	104.7	118.3	234.8	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB370C4-425AXSP06	-	122.4	89.8	103.3	216.3	-	123.8	91.7	104.9	216.2	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB550C4-525AXSP06	-	146.6	-	123.8	256.7	-	148.6	-	126	256.9	242	16.7	3"	194	10.9	3"	291	19.1	4"
EAW-FD15S2PB550C4-425AXSP06	-	135.4	99.2	114.2	240.2	-	137.3	101.4	116.1	240.5	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB370C5-625AXSP08	-	142.9	107.9	122.1	240.8	-	143.9	109.2	123.2	240.2	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB370C5-525AXSP08	84.60	137.7	103.4	117.5	235.6	86.5	138.7	104.7	118.3	234.8	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB370C5-425AXSP06	-	122.4	89.8	103.3	216.3	-	123.8	91.7	104.9	216.2	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB550C5-525AXSP06	-	146.6	-	123.8	256.7	-	148.6	-	126	256.9	242	16.7	3"	194	10.9	3"	291	19.1	4"
EAW-FD15S2PB550C5-425AXSP06	-	135.4	99.2	114.2	240.2	-	137.3	101.4	116.1	240.5	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB370K8-625AXSP08	-	142.6	107.7	121.8	240.3	-	143	108.7	122.5	239	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB370K8-525AXSP08	-	136	102.1	115.9	232.2	85.2	136.6	103.1	116.5	231	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB370K8-425AXSP06	-	119.7	-	101	211.2	-	121	-	102.3	210.9	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB550K8-625AXSP08	-	155.3	117.1	132.6	262.9	-	156	118.4	133.6	261.8	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB550K8-525AXSP08	90.70	148.2	110.9	126.2	254	92.7	148.9	112.3	127.2	252.7	182	18.8	3"	145	12.4	3"	218	26.4	3"
EAW-FD15S2PB550K8-425AXSP06	-	130.1	95.4	109.8	230.7	-	131.9	97.4	111.5	230.4	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S2PB750K8-625AXSP08	-	162.7	122.6	138.7	275.7	102.9	163.7	123.8	139.8	274.7	218	19.9	3"	174	13.1	3"	262	24.5	4"
EAW-FD15S2PB750K8-525AXSP06	-	148.4	-	125.5	260.3	-	150.5	-	127.5	260.3	242	16.7	3"	194	10.9	3"	291	19.1	4"
EAW-FD15S2PB750K8-425AXSP06	-	136.9	100.2	115.5	243.2	-	138.9	102.5	117.4	243.1	194	15.1	3"	155	9.9	3"	232	21.2	3"
EAW-FD15S3PB370K4-625AXSP06	135.80	215.9	164	185.1	362.2	138.1	216.5	165	185.5	359.8	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB370K4-525AXSP04	-	193.9	-	-	338.4	-	196.1	-	-	337.7	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB370K4-425AXSP04	-	178.2	-	150.4	315.3	-	180.2	-	152.6	314.3	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB550K4-625AXSP06	147.50	235.6	178.4	201.6	396.3	150.1	236.3	179.8	202.5	394.2	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB550K4-525AXSP04	-	210.9	-	178.5	369.8	-	213.4	-	181.1	369.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB550K4-425AXSP04	-	194.1	142	163.6	344.3	-	196.3	145.1	166	343.9	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB750K4-625AXSP04	-	231.9	-	-	402.5	-	234.9	-	-	402.2	436	16.2	4"	349	10.7	4"	523	17.9	(2) 4"
EAW-FD15S3PB750K4-525AXSP04	-	221.1	-	186.8	388.2	-	224.2	-	190	388.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB750K4-425AXSP04	-	203.7	149.1	171.9	362.3	-	206.8	152.5	174.9	362.9	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB370K5-625AXSP06	135.80	215.9	164	185.1	362.2	138.1	216.5	165	185.5	359.8	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB370K5-525AXSP04	-	193.9	-	-	338.4	-	196.1	-	-	337.7	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB370K5-425AXSP04	-	178.2	-	150.4	315.3	-	180.2	-	152.6	314.3	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB550K5-625AXSP06	147.50	235.6	178.4	201.6	396.3	150.1	236.3	179.8	202.5	394.2	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB550K5-525AXSP04	-	210.9	-	178.5	369.8	-	213.4	-	181.1	369.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB550K5-425AXSP04	-	194.1	142	163.6	344.3	-	196.3	145.1	166	343.9	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB750K5-625AXSP04	-	231.9	-	-	402.5	-	234.9	-	-	402.2	436	16.2	4"	349	10.7	4"	523	17.9	(2) 4"
EAW-FD15S3PB750K5-525AXSP04	-	221.1	-	186.8	388.2	-	224.2	-	190	388.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB750K5-425AXSP04	-	203.7	149.1	171.9	362.3	-	206.8	152.5	174.9	362.9	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB370C4-625AXSP06	136.30	216.7	164.3	185.5	363	138.7	217.5	166	186.7	361.6	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB370C4-525AXSP04	-	196.2	-	-	343.3	-	199.1	-	169	343.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB370C4-425AXSP04	-	182.2	-	153.8	322.4	-	184.7	136.5	156.1	322.3	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB550C4-525AXSP04	-	218.5	-	184.8	382.8	-	221.4	-	187.6	383.1	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB550C4-425AXSP04	-	201.5	147.4	170.1	357.9	-	204.4	150.9	172.8	358.4	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB370C5-625AXSP06	136.30	216.7	164.3	185.5	363	138.7	217.5	166	186.7	361.6	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB370C5-525AXSP04	-	196.2	-	-	343.3	-	199.1	-	169	343.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB370C5-425AXSP04	-	182.2	-	153.8	322.4	-	184.7	136.5	156.1	322.3	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB550C5-525AXSP04	-	218.5	-	184.8	382.8	-	221.4	-	187.6	383.1	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB550C5-425AXSP04	-	201.5	147.4	170.1	357.9	-	204.4	150.9	172.8	358.4	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB370K8-625AXSP06	135.80	215.9	164	185.1	362.2	138.1	216.5	165	185.5	359.8	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB370K8-525AXSP04	-	193.9	-	-	338.4	-	196.1	-	-	337.7	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB370K8-425AXSP04	-	178.2	-	150.4	315.3	-	180.2	-	152.6	314.3	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB550K8-625AXSP06	147.50	235.6	178.4	201.6	396.3	150.1	236.3	179.8	202.5	394.2	291	19.4	4"	232	15.6	3"	349	27.3	4"
EAW-FD15S3PB550K8-525AXSP04	-	210.9	-	178.5	369.8	-	213.4	-	181.1	369.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB550K8-425AXSP04	-	194.1	142	163.6	344.3	-	196.3	145.1	166	343.9	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S3PB750K8-625AXSP04	-	231.9	-	-	402.5	-	234.9	-	-	402.2	436	16.2	4"	349	10.7	4"	523	17.9	(2) 4"
EAW-FD15S3PB750K8-525AXSP04	-	221.1	-	186.8	388.2	-	224.2	-	190	388.2	363	14.8	4"	291	9.7	4"	436	20.9	4"
EAW-FD15S3PB750K8-425AXSP04	-	203.7	149.1	171.9	362.3	-	206.8	152.5	174.9	362.9	291	13.6	4"	232	11.8	3"	349	19.2	4"
EAW-FD15S4PB370K4-625AXSP04	-	282.9	213.4	241.5	477.7	-	283.7	215.5	242.9	475.1	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB370K4-525AXSP04	-	269.6	202.1	229.9	461.3	168.7	270.8	204.2	231.2	458.3	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB370K4-425AXSP04	150.20	248.2	184.9	210.9	429.7	153.4	249.3	187	212.2	427.6	291	17.1	4"	232	14.1	3"	349	24	4"
EAW-FD15S4PB550K4-625AXSP04	-	308.1	232	263.3	522.4	-	309.5	234.7	264.9	519.7	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB550K4-525AXSP04	179.40	293.7	219.9	249.8	503.7	183.4	295.1	222.4	251.8	502	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB550K4-425AXSP02	-	-	-	-	429.4	-	-	-	-	431.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB750K4-625AXSP04	-	322.6	242.8	275.4	547.9	203.8	324.6	245.8	277.6	545.9	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB750K4-525AXSP04	187.90	307.7	230.2	261.8	529	192.1	309.7	233.2	264.4	528	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB750K4-425AXSP02	-	-	-	-	451.8	-	-	-	-	455.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370K5-625AXSP04	-	282.9	213.4	241.5	477.7	-	283.7	215.5	242.9	475.1	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB370K5-525AXSP04	-	269.6	202.1	229.9	461.3	168.7	270.8	204.2	231.2	458.3	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB370K5-425AXSP04	150.20	248.2	184.9	210.9	429.7	153.4	249.3	187	212.2	427.6	291	17.1	4"	232	14.1	3"	349	24	4"
EAW-FD15S4PB550K5-625AXSP04	-	308.1	232	263.3	522.4	-	309.5	234.7	264.9	519.7	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB550K5-525AXSP04	179.40	293.7	219.9	249.8	503.7	183.4	295.1	222.4	251.8	502	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB550K5-425AXSP02	-	-	-	-	429.4	-	-	-	-	431.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB750K5-625AXSP04	-	322.6	242.8	275.4	547.9	203.8	324.6	245.8	277.6	545.9	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB750K5-525AXSP04	187.90	307.7	230.2	261.8	529	192.1	309.7	233.2	264.4	528	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB750K5-425AXSP02	-	-	-	-	451.8	-	-	-	-	455.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370C4-625AXSP04	-	283.5	213.8	242.3	478.7	-	285.4	216.8	244.4	477.5	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB370C4-525AXSP04	-	273.4	204.8	232.7	467.3	171.5	275	207.6	234.8	465.7	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB370C4-425AXSP02	-	-	-	-	402.8	-	-	-	-	405.2	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB550C4-525AXSP04	185.60	304	227.3	258.8	522.3	189.8	306.3	230.4	261.1	521	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB550C4-425AXSP02	-	-	-	-	446.6	-	-	-	-	450.1	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370C5-625AXSP04	-	283.5	213.8	242.3	478.7	-	285.4	216.8	244.4	477.5	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB370C5-525AXSP04	-	273.4	204.8	232.7	467.3	171.5	275	207.6	234.8	465.7	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB370C5-425AXSP02	-	-	-	-	402.8	-	-	-	-	405.2	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"

Note: "-" indicates flow rate is outside of unit capability

EAW-FD15S4PB550C5-525AXSP04	185.60	304	227.3	258.8	522.3	189.8	306.3	230.4	261.1	521	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB550C5-425AXSP02	-	-	-	-	446.6	-	-	-	-	450.1	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB370K8-625AXSP04	-	282.9	213.4	241.5	477.7	-	283.7	215.5	242.9	475.1	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB370K8-525AXSP04	-	269.6	202.1	229.9	461.3	168.7	270.8	204.2	231.2	458.3	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB370K8-425AXSP04	150.20	248.2	184.9	210.9	429.7	153.4	249.3	187	212.2	427.6	291	17.1	4"	232	14.1	3"	349	24	4"
EAW-FD15S4PB550K8-625AXSP04	-	308.1	232	263.3	522.4	-	309.5	234.7	264.9	519.7	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB550K8-525AXSP04	179.40	293.7	219.9	249.8	503.7	183.4	295.1	222.4	251.8	502	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB550K8-425AXSP02	-	-	-	-	429.4	-	-	-	-	431.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S4PB750K8-625AXSP04	-	322.6	242.8	275.4	547.9	203.8	324.6	245.8	277.6	545.9	436	19.7	4"	349	13	4"	523	22.7	(2) 4"
EAW-FD15S4PB750K8-525AXSP04	187.90	307.7	230.2	261.8	529	192.1	309.7	233.2	264.4	528	363	18.3	4"	291	12	4"	436	25.7	4"
EAW-FD15S4PB750K8-425AXSP02	-	-	-	-	451.8	-	-	-	-	455.6	581	9.6	(2) 4"	465	6.3	(2) 4"	698	13.5	(2) 4"
EAW-FD15S5PB370K4-625AXSP04	229.60	361.8	275.7	310.3	604.5	232.5	362.2	277	311	599.6	436	23.1	4"	349	15.2	4"	523	27.5	(2) 4"
EAW-FD15S5PB370K4-525AXSP02	-	-	-	-	545.3	-	-	-	-	546	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370K4-425AXSP02	-	279.9	-	-	506.2	-	285.1	-	-	506.6	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB550K4-625AXSP02	-	-	-	-	620.1	-	-	-	-	620.5	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	15.9	(3) 4"
EAW-FD15S5PB550K4-525AXSP02	-	-	-	-	595.2	-	338.6	-	-	596.3	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550K4-425AXSP02	-	304.5	-	-	551.9	-	310.6	-	-	553.5	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB750K4-625AXSP02	-	-	-	-	649.8	-	-	-	-	651.3	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	15.9	(3) 4"
EAW-FD15S5PB750K4-525AXSP02	-	348	-	-	624.4	-	355.4	-	-	626.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB750K4-425AXSP02	-	319.8	-	-	581.2	-	326.8	-	274.5	583.6	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB370K5-625AXSP04	229.60	361.8	275.7	310.3	604.5	232.5	362.2	277	311	599.6	436	23.1	4"	349	15.2	4"	523	27.5	(2) 4"
EAW-FD15S5PB370K5-525AXSP02	-	-	-	-	545.3	-	-	-	-	546	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370K5-425AXSP02	-	279.9	-	-	506.2	-	285.1	-	-	506.6	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB550K5-625AXSP02	-	-	-	-	620.1	-	-	-	-	620.5	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	15.9	(3) 4"
EAW-FD15S5PB550K5-525AXSP02	-	-	-	-	595.2	-	338.6	-	-	596.3	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550K5-425AXSP02	-	304.5	-	-	551.9	-	310.6	-	-	553.5	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB750K5-625AXSP02	-	-	-	-	649.8	-	-	-	-	651.3	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	15.9	(3) 4"
EAW-FD15S5PB750K5-525AXSP02	-	348	-	-	624.4	-	355.4	-	-	626.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB750K5-425AXSP02	-	319.8	-	-	581.2	-	326.8	-	274.5	583.6	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB370C4-625AXSP04	230.00	363.1	276.3	311.3	605.8	233.6	364	278.3	312.4	603.4	436	23.1	4"	349	15.2	4"	523	27.5	(2) 4"
EAW-FD15S5PB370C4-525AXSP02	-	-	-	-	553.1	-	-	-	-	554.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370C4-425AXSP02	-	286	-	-	518.2	-	292.2	-	-	519.2	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB550C4-525AXSP02	-	343.5	-	-	616.8	-	351	-	-	618.5	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550C4-425AXSP02	-	316.4	-	-	574.4	-	323.2	-	271.6	576.5	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB370C5-625AXSP04	230.00	363.1	276.3	311.3	605.8	233.6	364	278.3	312.4	603.4	436	23.1	4"	349	15.2	4"	523	27.5	(2) 4"
EAW-FD15S5PB370C5-525AXSP02	-	-	-	-	553.1	-	-	-	-	554.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370C5-425AXSP02	-	286	-	-	518.2	-	292.2	-	-	519.2	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB550C5-525AXSP02	-	343.5	-	-	616.8	-	351	-	-	618.5	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550C5-425AXSP02	-	316.4	-	-	574.4	-	323.2	-	271.6	576.5	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB370K8-625AXSP04	229.60	361.8	275.7	310.3	604.5	232.5	362.2	277	311	599.6	436	23.1	4"	349	15.2	4"	523	27.5	(2) 4"
EAW-FD15S5PB370K8-525AXSP02	-	-	-	-	545.3	-	-	-	-	546	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB370K8-425AXSP02	-	279.9	-	-	506.2	-	285.1	-	-	506.6	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB550K8-625AXSP02	-	-	-	-	620.1	-	-	-	-	620.5	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	15.9	(3) 4"
EAW-FD15S5PB550K8-525AXSP02	-	-	-	-	595.2	-	338.6	-	-	596.3	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB550K8-425AXSP02	-	304.5	-	-	551.9	-	310.6	-	-	553.5	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-FD15S5PB750K8-625AXSP02	-	-	-	-	649.8	-	-	-	-	651.3	872	13.9	(2) 4"	698	9.1	(2) 4"	1046	15.9	(3) 4"
EAW-FD15S5PB750K8-525AXSP02	-	348	-	-	624.4	-	355.4	-	-	626.7	727	12.5	(2) 4"	581	8.2	(2) 4"	872	17.6	(2) 4"
EAW-FD15S5PB750K8-425AXSP02	-	319.8	-	-	581.2	-	326.8	-	274.5	583.6	581	11.3	(2) 4"	465	7.4	(2) 4"	698	15.9	(2) 4"
EAW-DD1504XL017G7-625AXSP08	413.60	662.2	500.7	566.6	1117.9	417.8	659.1	501.1	564.8	1103.3	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD1504XL017G7-525AXSP06	-	588	-	497.9	1021.9	-	588.4	-	500.2	1011.7	952	15.3	4"	762	10.1	4"	1143	21.5	4"
EAW-DD1508XL017G7-625AXSP04	821.60	1318.8	996.6	1128.1	2227.3	830.2	1312.8	997.7	1124.6	2198.3	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD1508XL017G7-525AXSP04	748.20	1212.8	912.1	1034.6	2073.1	755.8	1208.8	913.4	1032.9	2046.2	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD1512XL017G7-625AXSP02	-	1874	-	-	3234.1	-	1875.9	-	1596.8	3201.6	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD1512XL017G7-525AXSP02	-	1723.5	-	1459.5	3003.9	-	1725.7	-	1467.1	2979.4	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S1XL045M4-621AXSP08	-	624.8	474.2	535.2	1046.1	396.4	621.7	474.2	533.1	1032.5	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL045M4-621AXSP04	-	1244.7	942.8	1064.3	2087.2	-	1238.5	944.3	1061.8	2057.7	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL045M4-621AXSP04	1250.30	1932	1483.6	1662.5	-	1249.8	1913.8	1474	1648.3	-	1722	25.3	6"	1377	20.2	4"	2066	35.5	6"
EAW-DD33S1XL045M4-525AXSP08	356.40	575.1	433.3	491.3	978.4	359.9	572.6	433.3	489.8	965	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL045M4-625AXSP08	-	623	472.1	533.4	1046.9	-	620.1	471.8	531	1033.5	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL045M4-525AXSP04	708.90	1145	862.2	977.8	1948.8	716.1	1140	863.6	975	1924.9	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL045M4-625AXSP04	-	1240.8	939.8	1062.1	2088.6	-	1235.2	939.3	1057.4	2059.4	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL045M4-525AXSP02	-	1628	-	1380.3	2831.3	-	1630.6	-	1385.5	2801.8	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL045M4-625AXSP02	-	1763.8	-	-	3031.8	-	1765.5	-	-	3001.9	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL037M4-525AXSP08	341.10	549.6	414.1	468.8	930.9	344.4	546.3	414	467.5	918.3	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL037M4-625AXSP08	-	593.8	450.5	508.5	994.3	-	589.8	449.7	506.4	980.9	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL037M4-525AXSP04	678.60	1094.3	825.4	934.7	1856.8	685.4	1087.9	825.4	930.7	1831.8	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL037M4-625AXSP04	-	1182.8	895.6	1012.6	1983.8	-	1174.9	895.6	1008.6	1954.8	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL037M4-525AXSP02	-	1555.9	-	-	2696.1	-	1558.2	-	-	2668.4	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL037M4-625AXSP02	-	1681.2	-	-	2885.3	-	1683.4	-	-	2851.2	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL030M4-525AXSP08	328.00	527.1	397.6	450.4	890.7	330.8	523.7	397.9	448.1	878.3	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL030M4-625AXSP08	-	567.9	431.2	486.3	949.3	-	564.6	430.8	484.1	935.1	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL030M4-525AXSP04	-	1049.6	792.5	896.6	1776.7	-	1044.4	792	893.5	1752.1	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL030M4-625AXSP04	-	1131.4	858.6	968.4	1891.8	-	1123.4	858	964.2	1863.7	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL030M4-525AXSP02	-	1492	-	-	2581.6	-	1495.3	-	-	2553.7	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL030M4-625AXSP02	-	1609.9	-	-	2752.9	-	1611.1	-	-	2719.6	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL045N4-525AXSP08	346.70	558.6	421	477	948.5	350.1	555.3	421	474.8	934.2	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL045N4-625AXSP08	-	605.9	459.2	518.5	1016.8	-	601.6	459	516.2	1001.4	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL045N4-525AXSP04	689.60	1112.2	837.8	949.4	1889.3	696.6	1107.3	837.9	946.7	1863.5	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL045N4-625AXSP04	-	1206.9	914.2	1032.6	2026.1	-	1198.4	913.9	1028.1	1995.5	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL045N4-525AXSP02	-	1580.4	-	1341.7	2746.3	-	1582.8	-	1346.6	2713.8	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL045N4-625AXSP02	-	1714.6	-	-	2946	-	1716.3	-	-	2909.9	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL037N4-525AXSP08	337.40	542.9	409.4	463.4	918.9	340.3	539.2	409	461.6	905.7	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL037N4-625AXSP08	-	587.6	445.4	502.6	983.5	-	583	444.8	500.7	968	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL037N4-525AXSP04	671.30	1081	814.7	922.4	1832.9	677.3	1075.3	814	919	1806.7	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL037N4-625AXSP04	-	1168.9	886.8	1001	1959.8	-	1161.4	885.8	995.9	1931.4	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL037N4-525AXSP02	-	1535.2	-	-	2662	-	1538.5	-	-	2632.3	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL037N4-625AXSP02	-	1664.2	-	-	2850.7	-	1664.5	-	-	2817.5	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL030N4-525AXSP08	-	509.6	385.7	435.9	860.9	-	506.6	385	433.9	848.2	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL030N4-625AXSP08	-	549.7	417.9	471	917.7	-	545.7	417.6	468.9	902.9	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL030N4-525AXSP04	-	1016.4	767.7	867.9	1717.4	-	1010.3	766.4	864	1692.2	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL030N4-625AXSP04	-	1095.1	832.2	938.2	1829	-	1087.2	830.5	934	1799.5	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL030N4-525AXSP02	-	1446.1	-	-	2496.7	-	1445.6	-	-	2467.6	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL030N4-625AXSP02	-	-	-	-	2662.4	-	-	-	-	2630	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL045M5-525AXSP08	356.40	575.1	433.3	491.3	978.4	359.9	572.6	433.3	489.8	965	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL045M5-625AXSP08	-	623	472.1	533.4	1046.9	-	620.1	471.8	531	1033.5	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL045M5-525AXSP04	708.90	1145	862.2	977.8	1948.8	716.1	1140	863.6	975	1924.9	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL045M5-625AXSP04	-	1240.8	939.8	1062.1	2088.6	-	1235.2	939.3	1057.4	2059.4	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL045M5-525AXSP02	-	1628	-	1380.3	2831.3	-	1630.6	-	1385.5	2801.8	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL045M5-625AXSP02	-	1763.8	-	-	3031.8	-	1765.5	-	-	3001.9	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL037M5-525AXSP08	341.10	549.6	414.1	468.8	930.9	344.4	546.3	414	467.5	918.3	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL037M5-625AXSP08	-	593.8	450.5	508.5	994.3	-	589.8	449.7	506.4	980.9	855	19.4	4"	684	12.8	4"	1026	27.2	4"

Note: "-" indicates flow rate is outside of unit capability

EAW-DD33S2XL037M5-525AXSP04	678.60	1094.3	825.4	934.7	1856.8	685.4	1087.9	825.4	930.7	1831.8	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL037M5-625AXSP04	-	1182.8	895.6	1012.6	1983.8	-	1174.9	895.6	1008.6	1954.8	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL037M5-525AXSP02	-	1555.9	-	-	2696.1	-	1558.2	-	-	2668.4	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL037M5-625AXSP02	-	1681.2	-	-	2885.3	-	1683.4	-	-	2851.2	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL030M5-525AXSP08	328.00	527.1	397.6	450.4	890.7	330.8	523.7	397.9	448.1	878.3	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL030M5-625AXSP08	-	567.9	431.2	486.3	949.3	-	564.6	430.8	484.1	935.1	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL030M5-525AXSP04	-	1049.6	792.5	896.6	1776.7	-	1044.4	792	893.5	1752.1	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL030M5-625AXSP04	-	1131.4	858.6	968.4	1891.8	-	1123.4	858	964.2	1863.7	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL030M5-525AXSP02	-	1492	-	-	2581.6	-	1495.3	-	-	2553.7	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL030M5-625AXSP02	-	1609.9	-	-	2752.9	-	1611.1	-	-	2719.6	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL045N5-525AXSP08	346.70	558.6	421	477	948.5	350.1	555.3	421	474.8	934.2	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL045N5-625AXSP08	-	605.9	459.2	518.5	1016.8	-	601.6	459	516.2	1001.4	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL045N5-525AXSP04	689.60	1112.2	837.8	949.4	1889.3	696.6	1107.3	837.9	946.7	1863.5	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL045N5-625AXSP04	-	1206.9	914.2	1032.6	2026.1	-	1198.4	913.9	1028.1	1995.5	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL045N5-525AXSP02	-	1580.4	-	1341.7	2746.3	-	1582.8	-	1346.6	2713.8	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL045N5-625AXSP02	-	1714.6	-	-	2946	-	1716.3	-	-	2909.9	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL037N5-525AXSP08	337.40	542.9	409.4	463.4	918.9	340.3	539.2	409	461.6	905.7	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL037N5-625AXSP08	-	587.6	445.4	502.6	983.5	-	583	444.8	500.7	968	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL037N5-525AXSP04	671.30	1081	814.7	922.4	1832.9	677.3	1075.3	814	919	1806.7	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL037N5-625AXSP04	-	1168.9	886.8	1001	1959.8	-	1161.4	885.8	995.9	1931.4	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL037N5-525AXSP02	-	1535.2	-	-	2662	-	1538.5	-	-	2632.3	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL037N5-625AXSP02	-	1664.2	-	-	2850.7	-	1664.5	-	-	2817.5	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"
EAW-DD33S1XL030N5-525AXSP08	-	509.6	385.7	435.9	860.9	-	506.6	385	433.9	848.2	708	18.9	4"	567	12.5	4"	850	26.4	4"
EAW-DD33S1XL030N5-625AXSP08	-	549.7	417.9	471	917.7	-	545.7	417.6	468.9	902.9	855	19.4	4"	684	12.8	4"	1026	27.2	4"
EAW-DD33S2XL030N5-525AXSP04	-	1016.4	767.7	867.9	1717.4	-	1010.3	766.4	864	1692.2	1429	21	4"	1143	13.9	4"	1714	24.2	6"
EAW-DD33S2XL030N5-625AXSP04	-	1095.1	832.2	938.2	1829	-	1087.2	830.5	934	1799.5	1722	17.7	6"	1377	15.2	4"	2066	24.8	6"
EAW-DD33S3XL030N5-525AXSP02	-	1446.1	-	-	2496.7	-	1445.6	-	-	2467.6	2870	15.4	6"	2296	10.1	6"	3443	21.6	6"
EAW-DD33S3XL030N5-625AXSP02	-	-	-	-	2662.4	-	-	-	-	2630	3443	16.8	6"	2755	11.1	6"	4132	18.6	(2) 6"

Note: "-" indicates flow rate is outside of unit capability