

NOTES:

1. (M) - FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

**FACE 2
PLAN VIEW**

FACE 1

FACE 2

Dimensions and Labels for Face 2 Plan View:

- Overall Width: 20'-5/8" [6112]
- Overall Height: 217 5/8" [5528]
- Top Section Width: 57" [1448]
- Top Section Height: 5 1/8" [130]
- Top Section Inlet: (4) 4 [100] BFW INLET
- Top Section Outlet: (4) 4 [100] BFW OUTLET
- Top Section Vent: (4) 1/2 [15] FPT VENT
- Top Section Access Doors: ACCESS DOORS
- Top Section Crossover Piping: CROSSOVER PIPING
- Top Section Dimensions: 21 3/4" [552] *, 95 1/4" [2418] *, 56 1/4" [1427], 75 1/32" [1906], 86 1/8" [2188]
- Top Section Piping: (2) 3 [80] MPT OVERFLOW, (2) 2 [50] MPT MAKE-UP, (2) 3 [80] MPT DRAIN
- Top Section Piping Dimensions: 6 7/8" [175], 33 1/2" [851] *, 5 1/2" [140], 5 7/8" [149] *, 25 1/4" [641], 5 1/4" [133], 4 1/4" [108], 117 3/4" [2991]
- Top Section Piping Dimensions: 3 5/8" [92], 16 7/8" [429], 46" [1168]

SHIPPING WEIGHT	38890 lbs+ [17645] kg+	OPERATING WEIGHT	57110 lbs+ [25905] kg+	HEAVIEST SECTION WEIGHT	12400 lbs+ [5625] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SFR
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----