

UNIT CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div>evapco</div>	DWG. # WB3241206-DRD-SF	REV. -
MODEL # eco-ATWB 24-3M12-Z	SCALE NTS		SERIAL #	DATE 9/17/2025
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</div> <div>7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.</div> <div>8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]</div>				
<div><div>FACE B</div><div>PLAN VIEW</div></div>			<div><div>FACE C</div><div>(2) ACCESS DOOR</div><div>FACE D</div><div>FACE A</div></div>	
<div><div>FACE B</div><div><div>(8) 4" [100] BFW FLUID IN</div><div>1'-10 1/4" [565] *</div><div>2'-1 1/4" [643]</div><div>3 5/8" [92]</div><div>(2) 3" [80] MPT OVERFLOW</div><div>(2) 2" [50] MPT MAKE-UP</div><div>(2) 3" [80] MPT DRAIN</div><div>5 1/8" [130]</div><div>24'-1 1/8" [7344]</div></div></div>			<div><div>FACE A</div><div><div>1'-3 1/4" [387]</div><div>(8) 1/2" [15] FPT VENT</div><div>SERIES FLOW PIPING (SEE NOTE 7)</div><div>AUX. CROSSOVER DRAIN (SEE NOTE 7)</div><div>1'-6 1/2" [470]</div><div>11'-11 3/4" [3651]</div></div></div>	
SHIPPING WEIGHT 34180 lbs+ [15505] kg+		OPERATING WEIGHT 51420 lbs+ [23325] kg+	HEAVIEST SECTION WEIGHT 14380 lbs+ [6525] kg+	NO. OF SHIPPING SECTIONS 4
DRAWN BY: JLG				