


EVAPCO, INC.




UNIT	CLOSED CIRCUIT COOLER	MODEL #	eco-ATWB-E 10-312	SCALE	N.T.S.	DWG. #	EGETM1206-DRB-ST	REV.	-	DATE	4/27/2024	SERIAL #	
------	-----------------------	---------	-------------------	-------	--------	--------	------------------	------	---	------	-----------	----------	--

- NOTES:
- (M)- FAN MOTOR LOCATION
 - HEAVIEST SECTION IS UPPER SECTION
 - MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
 - +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
 - MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
 - *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
 - VENT PROVIDED ON CLOSED CIRCUIT COOLERS ONLY

**FACE 2
PLAN VIEW**




FACE 1



FACE 2

(2) 1/2 [15]
FPT VENT
(CLOSED CIRCUIT
COOLERS ONLY)



FACE 1

SHIPPING WEIGHT	14980 lbs+ [6795] kg+	OPERATING WEIGHT	22490 lbs+ [10205] kg+	HEAVIEST SECTION WEIGHT	12250 lbs+ [5560] kg+	NO. OF SHIPPING SECTIONS	2
-----------------	-----------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---