

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
-	-	-	ATWB 3-2C3-Z	130	4.2
-	-	-	ATWB 3-3C3-Z	130	6.0
-	-	-	ATWB 3-4C3-Z	130	7.7
-	-	-	ATWB 3-4D3-Z	130	7.7
-	-	-	ATWB 3-5C3-Z	130	9.4
-	-	-	ATWB 3-5D3-Z	130	9.4
-	-	-	ATWB 4-2E4-Z	185	5.3
-	-	-	ATWB 4-3E4-Z	185	7.2
-	-	-	ATWB 4-4E4-Z	185	9.1
-	-	-	ATWB 4-4F4-Z	185	9.1
-	-	-	ATWB 4-5E4-Z	185	10.9
-	-	-	ATWB 4-5F4-Z	185	10.9
ATWB 4-3E6	370	3.8	ATWB 4-3E6-Z	185	8.1
ATWB 4-3F6	370	3.8	ATWB 4-3F6-Z	185	8.1
ATWB 4-3G6	370	3.8	ATWB 4-3G6-Z	185	8.1
ATWB 4-4E6	370	4.9	ATWB 4-4E6-Z	185	10.2
ATWB 4-4F6	370	4.9	ATWB 4-4F6-Z	185	10.2
ATWB 4-4G6	370	4.9	ATWB 4-4G6-Z	185	10.2
ATWB 4-5E6	370	5.9	ATWB 4-5E6-Z	185	12.4
ATWB 4-5F6	370	5.9	ATWB 4-5F6-Z	185	12.4
ATWB 4-5G6	370	5.9	ATWB 4-5G6-Z	185	12.4
ATWB 4-3E9	370	4.5	ATWB 4-3E9-Z	185	9.4
ATWB 4-3F9	370	4.5	ATWB 4-3F9-Z	185	9.4
ATWB 4-4E9	370	5.7	ATWB 4-4E9-Z	185	12.0
ATWB 4-4F9	370	5.7	ATWB 4-4F9-Z	185	12.0
ATWB 4-5E9	370	7.0	ATWB 4-5E9-Z	185	14.6
ATWB 4-5F9	370	7.0	ATWB 4-5F9-Z	185	14.6
ATWB 4-3E12	370	5.1	ATWB 4-3E12-Z	185	10.7
ATWB 4-3F12	370	5.1	ATWB 4-3F12-Z	185	10.7
ATWB 4-3G12	370	5.1	ATWB 4-3G12-Z	185	10.7
ATWB 4-4E12	370	6.5	ATWB 4-4E12-Z	185	13.7
ATWB 4-4F12	370	6.5	ATWB 4-4F12-Z	185	13.7
ATWB 4-4G12	370	6.5	ATWB 4-4G12-Z	185	13.7
ATWB 4-5E12	370	8.0	ATWB 4-5E12-Z	185	16.8
ATWB 4-5F12	370	8.0	ATWB 4-5F12-Z	185	16.8
ATWB 4-5G12	370	8.0	ATWB 4-5G12-Z	185	16.8
ATWB 9-3G8	370	1.3	ATWB 9-3G8-Z	185	2.6
ATWB 9-3H8	370	1.3	ATWB 9-3H8-Z	185	2.6
ATWB 9-3I8	370	1.3	ATWB 9-3I8-Z	185	2.6
ATWB 9-3J8	370	1.3	ATWB 9-3J8-Z	185	2.6
ATWB 9-4G8	370	1.6	ATWB 9-4G8-Z	185	3.4
ATWB 9-4H8	370	1.6	ATWB 9-4H8-Z	185	3.4
ATWB 9-4I8	370	1.6	ATWB 9-4I8-Z	185	3.4
ATWB 9-4J8	370	1.6	ATWB 9-4J8-Z	185	3.4
ATWB 9-5H8	370	1.9	ATWB 9-5H8-Z	185	4.1
ATWB 9-5I8	370	1.9	ATWB 9-5I8-Z	185	4.1
ATWB 9-5J8	370	1.9	ATWB 9-5J8-Z	185	4.1
ATWB 9-6H8	370	2.3	ATWB 9-6H8-Z	185	4.8
ATWB 9-6I8	370	2.3	ATWB 9-6I8-Z	185	4.8
ATWB 9-6J8	370	2.3	ATWB 9-6J8-Z	185	4.8
ATWB 9-7H8	370	2.6	ATWB 9-7H8-Z	185	5.5
ATWB 9-7I8	370	2.6	ATWB 9-7I8-Z	185	5.5
ATWB 9-7J8	370	2.6	ATWB 9-7J8-Z	185	5.5
ATWB 9-3H9	400	1.3	ATWB 9-3H9-Z	200	2.8

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 9-3I9	400	1.3	ATWB 9-3I9-Z	200	2.8
ATWB 9-3J9	400	1.3	ATWB 9-3J9-Z	200	2.8
ATWB 9-3K9	400	1.3	ATWB 9-3K9-Z	200	2.8
ATWB 9-4H9	400	1.7	ATWB 9-4H9-Z	200	3.5
ATWB 9-4I9	400	1.7	ATWB 9-4I9-Z	200	3.5
ATWB 9-4J9	400	1.7	ATWB 9-4J9-Z	200	3.5
ATWB 9-4K9	400	1.7	ATWB 9-4K9-Z	200	3.5
ATWB 9-5H9	400	2.0	ATWB 9-5H9-Z	200	4.3
ATWB 9-5I9	400	2.0	ATWB 9-5I9-Z	200	4.3
ATWB 9-5J9	400	2.0	ATWB 9-5J9-Z	200	4.3
ATWB 9-5K9	400	2.0	ATWB 9-5K9-Z	200	4.3
ATWB 9-6I9	400	2.4	ATWB 9-6I9-Z	200	5.0
ATWB 9-6J9	400	2.4	ATWB 9-6J9-Z	200	5.0
ATWB 9-6K9	400	2.4	ATWB 9-6K9-Z	200	5.0
ATWB 9-7I9	400	2.7	ATWB 9-7I9-Z	200	5.8
ATWB 9-7J9	400	2.7	ATWB 9-7J9-Z	200	5.8
ATWB 9-7K9	400	2.7	ATWB 9-7K9-Z	200	5.8
ATWB 9-3H11	400	1.4	ATWB 9-3H11-Z	200	3.0
ATWB 9-3I11	400	1.4	ATWB 9-3I11-Z	200	3.0
ATWB 9-3J11	400	1.4	ATWB 9-3J11-Z	200	3.0
ATWB 9-3K11	400	1.4	ATWB 9-3K11-Z	200	3.0
ATWB 9-4H11	400	1.8	ATWB 9-4H11-Z	200	3.8
ATWB 9-4I11	400	1.8	ATWB 9-4I11-Z	200	3.8
ATWB 9-4J11	400	1.8	ATWB 9-4J11-Z	200	3.8
ATWB 9-4K11	400	1.8	ATWB 9-4K11-Z	200	3.8
ATWB 9-5I11	400	2.2	ATWB 9-5I11-Z	200	4.6
ATWB 9-5J11	400	2.2	ATWB 9-5J11-Z	200	4.6
ATWB 9-5K11	400	2.2	ATWB 9-5K11-Z	200	4.6
ATWB 9-5L11	400	2.2	ATWB 9-5L11-Z	200	4.6
ATWB 9-6J11	400	2.6	ATWB 9-6J11-Z	200	5.4
ATWB 9-6K11	400	2.6	ATWB 9-6K11-Z	200	5.4
ATWB 9-6L11	400	2.6	ATWB 9-6L11-Z	200	5.4
ATWB 9-7J11	400	3.0	ATWB 9-7J11-Z	200	6.2
ATWB 9-7K11	400	3.0	ATWB 9-7K11-Z	200	6.2
ATWB 9-7L11	400	3.0	ATWB 9-7L11-Z	200	6.2
ATWB 9-3I12	400	1.5	ATWB 9-3I12-Z	200	3.1
ATWB 9-3J12	400	1.5	ATWB 9-3J12-Z	200	3.1
ATWB 9-3K12	400	1.5	ATWB 9-3K12-Z	200	3.1
ATWB 9-3L12	400	1.5	ATWB 9-3L12-Z	200	3.1
ATWB 9-4I12	400	1.9	ATWB 9-4I12-Z	200	4.0
ATWB 9-4J12	400	1.9	ATWB 9-4J12-Z	200	4.0
ATWB 9-4K12	400	1.9	ATWB 9-4K12-Z	200	4.0
ATWB 9-4L12	400	1.9	ATWB 9-4L12-Z	200	4.0
ATWB 9-5J12	400	2.3	ATWB 9-5J12-Z	200	4.9
ATWB 9-5K12	400	2.3	ATWB 9-5K12-Z	200	4.9
ATWB 9-5L12	400	2.3	ATWB 9-5L12-Z	200	4.9
ATWB 9-5M12	400	2.3	ATWB 9-5M12-Z	200	4.9
ATWB 9-6J12	400	2.7	ATWB 9-6J12-Z	200	5.8
ATWB 9-6K12	400	2.7	ATWB 9-6K12-Z	200	5.8
ATWB 9-6L12	400	2.7	ATWB 9-6L12-Z	200	5.8
ATWB 9-6M12	400	2.7	ATWB 9-6M12-Z	200	5.8
ATWB 9-7J12	400	3.2	ATWB 9-7J12-Z	200	6.6
ATWB 9-7K12	400	3.2	ATWB 9-7K12-Z	200	6.6
ATWB 9-7L12	400	3.2	ATWB 9-7L12-Z	200	6.6

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 9-7M12	400	3.2	ATWB 9-7M12-Z	200	6.6
ATWB 9-3I14	400	1.6	ATWB 9-3I14-Z	200	3.4
ATWB 9-3J14	400	1.6	ATWB 9-3J14-Z	200	3.4
ATWB 9-3K14	400	1.6	ATWB 9-3K14-Z	200	3.4
ATWB 9-3L14	400	1.6	ATWB 9-3L14-Z	200	3.4
ATWB 9-4J14	400	2.1	ATWB 9-4J14-Z	200	4.4
ATWB 9-4K14	400	2.1	ATWB 9-4K14-Z	200	4.4
ATWB 9-4L14	400	2.1	ATWB 9-4L14-Z	200	4.4
ATWB 9-4M14	400	2.1	ATWB 9-4M14-Z	200	4.4
ATWB 9-5J14	400	2.5	ATWB 9-5J14-Z	200	5.3
ATWB 9-5K14	400	2.5	ATWB 9-5K14-Z	200	5.3
ATWB 9-5L14	400	2.5	ATWB 9-5L14-Z	200	5.3
ATWB 9-5M14	400	2.5	ATWB 9-5M14-Z	200	5.3
ATWB 9-6K14	400	3.0	ATWB 9-6K14-Z	200	6.3
ATWB 9-6L14	400	3.0	ATWB 9-6L14-Z	200	6.3
ATWB 9-6M14	400	3.0	ATWB 9-6M14-Z	200	6.3
ATWB 9-7K14	400	3.4	ATWB 9-7K14-Z	200	7.2
ATWB 9-7L14	400	3.4	ATWB 9-7L14-Z	200	7.2
ATWB 9-7M14	400	3.4	ATWB 9-7M14-Z	200	7.2
ATWB 9-3H18	400	1.9	ATWB 9-3H18-Z	200	3.9
ATWB 9-3I18	400	1.9	ATWB 9-3I18-Z	200	3.9
ATWB 9-3J18	400	1.9	ATWB 9-3J18-Z	200	3.9
ATWB 9-3K18	400	1.9	ATWB 9-3K18-Z	200	3.9
ATWB 9-4H18	400	2.4	ATWB 9-4H18-Z	200	5.0
ATWB 9-4I18	400	2.4	ATWB 9-4I18-Z	200	5.0
ATWB 9-4J18	400	2.4	ATWB 9-4J18-Z	200	5.0
ATWB 9-4K18	400	2.4	ATWB 9-4K18-Z	200	5.0
ATWB 9-5H18	400	2.9	ATWB 9-5H18-Z	200	6.2
ATWB 9-5I18	400	2.9	ATWB 9-5I18-Z	200	6.2
ATWB 9-5J18	400	2.9	ATWB 9-5J18-Z	200	6.2
ATWB 9-5K18	400	2.9	ATWB 9-5K18-Z	200	6.2
ATWB 9-6I18	400	3.5	ATWB 9-6I18-Z	200	7.3
ATWB 9-6J18	400	3.5	ATWB 9-6J18-Z	200	7.3
ATWB 9-6K18	400	3.5	ATWB 9-6K18-Z	200	7.3
ATWB 9-7I18	400	4.0	ATWB 9-7I18-Z	200	8.4
ATWB 9-7J18	400	4.0	ATWB 9-7J18-Z	200	8.4
ATWB 9-7K18	400	4.0	ATWB 9-7K18-Z	200	8.4
ATWB 9-3H21	400	2.0	ATWB 9-3H21-Z	200	4.3
ATWB 9-3I21	400	2.0	ATWB 9-3I21-Z	200	4.3
ATWB 9-3J21	400	2.0	ATWB 9-3J21-Z	200	4.3
ATWB 9-3K21	400	2.0	ATWB 9-3K21-Z	200	4.3
ATWB 9-4H21	400	2.6	ATWB 9-4H21-Z	200	5.5
ATWB 9-4I21	400	2.6	ATWB 9-4I21-Z	200	5.5
ATWB 9-4J21	400	2.6	ATWB 9-4J21-Z	200	5.5
ATWB 9-4K21	400	2.6	ATWB 9-4K21-Z	200	5.5
ATWB 9-5I21	400	3.2	ATWB 9-5I21-Z	200	6.8
ATWB 9-5J21	400	3.2	ATWB 9-5J21-Z	200	6.8
ATWB 9-5K21	400	3.2	ATWB 9-5K21-Z	200	6.8
ATWB 9-5L21	400	3.2	ATWB 9-5L21-Z	200	6.8
ATWB 9-6J21	400	3.8	ATWB 9-6J21-Z	200	8.0
ATWB 9-6K21	400	3.8	ATWB 9-6K21-Z	200	8.0
ATWB 9-6L21	400	3.8	ATWB 9-6L21-Z	200	8.0
ATWB 9-7J21	400	4.4	ATWB 9-7J21-Z	200	9.3
ATWB 9-7K21	400	4.4	ATWB 9-7K21-Z	200	9.3

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 9-7L21	400	4.4	ATWB 9-7L21-Z	200	9.3
ATWB 17-3I12	400	0.4	ATWB 17-3I12-Z	200	0.9
ATWB 17-3J12	400	0.4	ATWB 17-3J12-Z	200	0.9
ATWB 17-3K12	400	0.4	ATWB 17-3K12-Z	200	0.9
ATWB 17-3L12	400	0.4	ATWB 17-3L12-Z	200	0.9
ATWB 17-4I12	400	0.5	ATWB 17-4I12-Z	200	1.2
ATWB 17-4J12	400	0.5	ATWB 17-4J12-Z	200	1.2
ATWB 17-4K12	400	0.5	ATWB 17-4K12-Z	200	1.2
ATWB 17-4L12	400	0.5	ATWB 17-4L12-Z	200	1.2
ATWB 17-5J12	400	0.7	ATWB 17-5J12-Z	200	1.4
ATWB 17-5K12	400	0.7	ATWB 17-5K12-Z	200	1.4
ATWB 17-5L12	400	0.7	ATWB 17-5L12-Z	200	1.4
ATWB 17-5M12	400	0.7	ATWB 17-5M12-Z	200	1.4
ATWB 17-6J12	400	0.8	ATWB 17-6J12-Z	200	1.7
ATWB 17-6K12	400	0.8	ATWB 17-6K12-Z	200	1.7
ATWB 17-6L12	400	0.8	ATWB 17-6L12-Z	200	1.7
ATWB 17-6M12	400	0.8	ATWB 17-6M12-Z	200	1.7
ATWB 17-7J12	400	0.9	ATWB 17-7J12-Z	200	1.9
ATWB 17-7K12	400	0.9	ATWB 17-7K12-Z	200	1.9
ATWB 17-7L12	400	0.9	ATWB 17-7L12-Z	200	1.9
ATWB 17-7M12	400	0.9	ATWB 17-7M12-Z	200	1.9
ATWB 17-3I14	400	0.5	ATWB 17-3I14-Z	200	1.0
ATWB 17-3J14	400	0.5	ATWB 17-3J14-Z	200	1.0
ATWB 17-3K14	400	0.5	ATWB 17-3K14-Z	200	1.0
ATWB 17-3L14	400	0.5	ATWB 17-3L14-Z	200	1.0
ATWB 17-4J14	400	0.6	ATWB 17-4J14-Z	200	1.3
ATWB 17-4K14	400	0.6	ATWB 17-4K14-Z	200	1.3
ATWB 17-4L14	400	0.6	ATWB 17-4L14-Z	200	1.3
ATWB 17-4M14	400	0.6	ATWB 17-4M14-Z	200	1.3
ATWB 17-5J14	400	0.7	ATWB 17-5J14-Z	200	1.5
ATWB 17-5K14	400	0.7	ATWB 17-5K14-Z	200	1.5
ATWB 17-5L14	400	0.7	ATWB 17-5L14-Z	200	1.5
ATWB 17-5M14	400	0.7	ATWB 17-5M14-Z	200	1.5
ATWB 17-6K14	400	0.9	ATWB 17-6K14-Z	200	1.8
ATWB 17-6L14	400	0.9	ATWB 17-6L14-Z	200	1.8
ATWB 17-6M14	400	0.9	ATWB 17-6M14-Z	200	1.8
ATWB 17-7K14	400	1.0	ATWB 17-7K14-Z	200	2.1
ATWB 17-7L14	400	1.0	ATWB 17-7L14-Z	200	2.1
ATWB 17-7M14	400	1.0	ATWB 17-7M14-Z	200	2.1
ATWB 12-3J12	580	1.8	ATWB 12-3J12-Z	290	3.7
ATWB 12-3K12	580	1.8	ATWB 12-3K12-Z	290	3.7
ATWB 12-3L12	580	1.8	ATWB 12-3L12-Z	290	3.7
ATWB 12-3M12	580	1.8	ATWB 12-3M12-Z	290	3.7
ATWB 12-4J12	580	2.2	ATWB 12-4J12-Z	290	4.6
ATWB 12-4K12	580	2.2	ATWB 12-4K12-Z	290	4.6
ATWB 12-4L12	580	2.2	ATWB 12-4L12-Z	290	4.6
ATWB 12-4M12	580	2.2	ATWB 12-4M12-Z	290	4.6
ATWB 12-4N12	580	2.2	ATWB 12-4N12-Z	290	4.6
ATWB 12-5K12	580	2.6	ATWB 12-5K12-Z	290	5.4
ATWB 12-5L12	580	2.6	ATWB 12-5L12-Z	290	5.4
ATWB 12-5M12	580	2.6	ATWB 12-5M12-Z	290	5.4
ATWB 12-5N12	580	2.6	ATWB 12-5N12-Z	290	5.4
ATWB 12-6L12	580	3.0	ATWB 12-6L12-Z	290	6.3
ATWB 12-6M12	580	3.0	ATWB 12-6M12-Z	290	6.3

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 12-6N12	580	3.0	ATWB 12-6N12-Z	290	6.3
ATWB 12-7L12	580	3.4	ATWB 12-7L12-Z	290	7.2
ATWB 12-7M12	580	3.4	ATWB 12-7M12-Z	290	7.2
ATWB 12-7N12	580	3.4	ATWB 12-7N12-Z	290	7.2
ATWB 12-3K14	580	1.9	ATWB 12-3K14-Z	290	3.9
ATWB 12-3L14	580	1.9	ATWB 12-3L14-Z	290	3.9
ATWB 12-3M14	580	1.9	ATWB 12-3M14-Z	290	3.9
ATWB 12-3N14	580	1.9	ATWB 12-3N14-Z	290	3.9
ATWB 12-4K14	580	2.3	ATWB 12-4K14-Z	290	4.9
ATWB 12-4L14	580	2.3	ATWB 12-4L14-Z	290	4.9
ATWB 12-4M14	580	2.3	ATWB 12-4M14-Z	290	4.9
ATWB 12-4N14	580	2.3	ATWB 12-4N14-Z	290	4.9
ATWB 12-5L14	580	2.8	ATWB 12-5L14-Z	290	5.9
ATWB 12-5M14	580	2.8	ATWB 12-5M14-Z	290	5.9
ATWB 12-5N14	580	2.8	ATWB 12-5N14-Z	290	5.9
ATWB 12-6L14	580	3.3	ATWB 12-6L14-Z	290	6.8
ATWB 12-6M14	580	3.3	ATWB 12-6M14-Z	290	6.8
ATWB 12-6N14	580	3.3	ATWB 12-6N14-Z	290	6.8
ATWB 12-7L14	580	3.7	ATWB 12-7L14-Z	290	7.8
ATWB 12-7M14	580	3.7	ATWB 12-7M14-Z	290	7.8
ATWB 12-7N14	580	3.7	ATWB 12-7N14-Z	290	7.8
ATWB 12-3K18	580	2.1	ATWB 12-3K18-Z	290	4.5
ATWB 12-3L18	580	2.1	ATWB 12-3L18-Z	290	4.5
ATWB 12-3M18	580	2.1	ATWB 12-3M18-Z	290	4.5
ATWB 12-3N18	580	2.1	ATWB 12-3N18-Z	290	4.5
ATWB 12-4K18	580	2.7	ATWB 12-4K18-Z	290	5.6
ATWB 12-4L18	580	2.7	ATWB 12-4L18-Z	290	5.6
ATWB 12-4M18	580	2.7	ATWB 12-4M18-Z	290	5.6
ATWB 12-4N18	580	2.7	ATWB 12-4N18-Z	290	5.6
ATWB 12-4O18	580	2.7	ATWB 12-4O18-Z	290	5.6
ATWB 12-5L18	580	3.2	ATWB 12-5L18-Z	290	6.7
ATWB 12-5M18	580	3.2	ATWB 12-5M18-Z	290	6.7
ATWB 12-5N18	580	3.2	ATWB 12-5N18-Z	290	6.7
ATWB 12-5O18	580	3.2	ATWB 12-5O18-Z	290	6.7
ATWB 12-6M18	580	3.7	ATWB 12-6M18-Z	290	7.8
ATWB 12-6N18	580	3.7	ATWB 12-6N18-Z	290	7.8
ATWB 12-6O18	580	3.7	ATWB 12-6O18-Z	290	7.8
ATWB 12-6P18	580	3.7	ATWB 12-6P18-Z	290	7.8
ATWB 12-7M18	580	4.3	ATWB 12-7M18-Z	290	9.0
ATWB 12-7N18	580	4.3	ATWB 12-7N18-Z	290	9.0
ATWB 12-7O18	580	4.3	ATWB 12-7O18-Z	290	9.0
ATWB 12-7P18	580	4.3	ATWB 12-7P18-Z	290	9.0
ATWB 12-3L20	580	2.2	ATWB 12-3L20-Z	290	4.7
ATWB 12-3M20	580	2.2	ATWB 12-3M20-Z	290	4.7
ATWB 12-3N20	580	2.2	ATWB 12-3N20-Z	290	4.7
ATWB 12-3O20	580	2.2	ATWB 12-3O20-Z	290	4.7
ATWB 12-4L20	580	2.8	ATWB 12-4L20-Z	290	5.9
ATWB 12-4M20	580	2.8	ATWB 12-4M20-Z	290	5.9
ATWB 12-4N20	580	2.8	ATWB 12-4N20-Z	290	5.9
ATWB 12-4O20	580	2.8	ATWB 12-4O20-Z	290	5.9
ATWB 12-5M20	580	3.4	ATWB 12-5M20-Z	290	7.1
ATWB 12-5N20	580	3.4	ATWB 12-5N20-Z	290	7.1
ATWB 12-5O20	580	3.4	ATWB 12-5O20-Z	290	7.1
ATWB 12-5P20	580	3.4	ATWB 12-5P20-Z	290	7.1

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 12-6N20	580	4.0	ATWB 12-6N20-Z	290	8.3
ATWB 12-6O20	580	4.0	ATWB 12-6O20-Z	290	8.3
ATWB 12-6P20	580	4.0	ATWB 12-6P20-Z	290	8.3
ATWB 12-7N20	580	4.5	ATWB 12-7N20-Z	290	9.6
ATWB 12-7O20	580	4.5	ATWB 12-7O20-Z	290	9.6
ATWB 12-7P20	580	4.5	ATWB 12-7P20-Z	290	9.6
ATWB 12-3J24	580	0.5	ATWB 12-3J24-Z	290	1.1
ATWB 12-3K24	580	0.5	ATWB 12-3K24-Z	290	1.1
ATWB 12-3L24	580	0.5	ATWB 12-3L24-Z	290	1.1
ATWB 12-3M24	580	0.5	ATWB 12-3M24-Z	290	1.1
ATWB 12-4K24	580	0.6	ATWB 12-4K24-Z	290	1.3
ATWB 12-4L24	580	0.6	ATWB 12-4L24-Z	290	1.3
ATWB 12-4M24	580	0.6	ATWB 12-4M24-Z	290	1.3
ATWB 12-4N24	580	0.6	ATWB 12-4N24-Z	290	1.3
ATWB 12-5K24	580	0.7	ATWB 12-5K24-Z	290	1.6
ATWB 12-5L24	580	0.7	ATWB 12-5L24-Z	290	1.6
ATWB 12-5M24	580	0.7	ATWB 12-5M24-Z	290	1.6
ATWB 12-5N24	580	0.7	ATWB 12-5N24-Z	290	1.6
ATWB 12-6L24	580	0.9	ATWB 12-6L24-Z	290	1.8
ATWB 12-6M24	580	0.9	ATWB 12-6M24-Z	290	1.8
ATWB 12-6N24	580	0.9	ATWB 12-6N24-Z	290	1.8
ATWB 12-7L24	580	1.0	ATWB 12-7L24-Z	290	2.1
ATWB 12-7M24	580	1.0	ATWB 12-7M24-Z	290	2.1
ATWB 12-7N24	580	1.0	ATWB 12-7N24-Z	290	2.1
ATWB 12-3K28	580	0.5	ATWB 12-3K28-Z	290	1.1
ATWB 12-3L28	580	0.5	ATWB 12-3L28-Z	290	1.1
ATWB 12-3M28	580	0.5	ATWB 12-3M28-Z	290	1.1
ATWB 12-3N28	580	0.5	ATWB 12-3N28-Z	290	1.1
ATWB 12-4K28	580	0.7	ATWB 12-4K28-Z	290	1.4
ATWB 12-4L28	580	0.7	ATWB 12-4L28-Z	290	1.4
ATWB 12-4M28	580	0.7	ATWB 12-4M28-Z	290	1.4
ATWB 12-4N28	580	0.7	ATWB 12-4N28-Z	290	1.4
ATWB 12-5L28	580	0.8	ATWB 12-5L28-Z	290	1.7
ATWB 12-5M28	580	0.8	ATWB 12-5M28-Z	290	1.7
ATWB 12-5N28	580	0.8	ATWB 12-5N28-Z	290	1.7
ATWB 12-6L28	580	0.9	ATWB 12-6L28-Z	290	2.0
ATWB 12-6M28	580	0.9	ATWB 12-6M28-Z	290	2.0
ATWB 12-6N28	580	0.9	ATWB 12-6N28-Z	290	2.0
ATWB 12-7L28	580	1.1	ATWB 12-7L28-Z	290	2.2
ATWB 12-7M28	580	1.1	ATWB 12-7M28-Z	290	2.2
ATWB 12-7N28	580	1.1	ATWB 12-7N28-Z	290	2.2
ATWB 12-3K36	580	0.6	ATWB 12-3K36-Z	290	1.3
ATWB 12-3L36	580	0.6	ATWB 12-3L36-Z	290	1.3
ATWB 12-3M36	580	0.6	ATWB 12-3M36-Z	290	1.3
ATWB 12-3N36	580	0.6	ATWB 12-3N36-Z	290	1.3
ATWB 12-4K36	580	0.8	ATWB 12-4K36-Z	290	1.6
ATWB 12-4L36	580	0.8	ATWB 12-4L36-Z	290	1.6
ATWB 12-4M36	580	0.8	ATWB 12-4M36-Z	290	1.6
ATWB 12-4N36	580	0.8	ATWB 12-4N36-Z	290	1.6
ATWB 12-4O36	580	0.8	ATWB 12-4O36-Z	290	1.6
ATWB 12-5L36	580	0.9	ATWB 12-5L36-Z	290	1.9
ATWB 12-5M36	580	0.9	ATWB 12-5M36-Z	290	1.9
ATWB 12-5N36	580	0.9	ATWB 12-5N36-Z	290	1.9
ATWB 12-5O36	580	0.9	ATWB 12-5O36-Z	290	1.9

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 12-6M36	580	1.1	ATWB 12-6M36-Z	290	2.3
ATWB 12-6N36	580	1.1	ATWB 12-6N36-Z	290	2.3
ATWB 12-6O36	580	1.1	ATWB 12-6O36-Z	290	2.3
ATWB 12-6P36	580	1.1	ATWB 12-6P36-Z	290	2.3
ATWB 12-7M36	580	1.2	ATWB 12-7M36-Z	290	2.6
ATWB 12-7N36	580	1.2	ATWB 12-7N36-Z	290	2.6
ATWB 12-7O36	580	1.2	ATWB 12-7O36-Z	290	2.6
ATWB 12-7P36	580	1.2	ATWB 12-7P36-Z	290	2.6
ATWB 12-3L40	580	0.6	ATWB 12-3L40-Z	290	1.4
ATWB 12-3M40	580	0.6	ATWB 12-3M40-Z	290	1.4
ATWB 12-3N40	580	0.6	ATWB 12-3N40-Z	290	1.4
ATWB 12-3O40	580	0.6	ATWB 12-3O40-Z	290	1.4
ATWB 12-4L40	580	0.8	ATWB 12-4L40-Z	290	1.7
ATWB 12-4M40	580	0.8	ATWB 12-4M40-Z	290	1.7
ATWB 12-4N40	580	0.8	ATWB 12-4N40-Z	290	1.7
ATWB 12-4O40	580	0.8	ATWB 12-4O40-Z	290	1.7
ATWB 12-5M40	580	1.0	ATWB 12-5M40-Z	290	2.0
ATWB 12-5N40	580	1.0	ATWB 12-5N40-Z	290	2.0
ATWB 12-5O40	580	1.0	ATWB 12-5O40-Z	290	2.0
ATWB 12-5P40	580	1.0	ATWB 12-5P40-Z	290	2.0
ATWB 12-6N40	580	1.1	ATWB 12-6N40-Z	290	2.4
ATWB 12-6O40	580	1.1	ATWB 12-6O40-Z	290	2.4
ATWB 12-6P40	580	1.1	ATWB 12-6P40-Z	290	2.4
ATWB 12-7N40	580	1.3	ATWB 12-7N40-Z	290	2.7
ATWB 12-7O40	580	1.3	ATWB 12-7O40-Z	290	2.7
ATWB 12-7P40	580	1.3	ATWB 12-7P40-Z	290	2.7
ATWB 24-3J12	580	0.5	ATWB 24-3J12-Z	290	1.1
ATWB 24-3K12	580	0.5	ATWB 24-3K12-Z	290	1.1
ATWB 24-3L12	580	0.5	ATWB 24-3L12-Z	290	1.1
ATWB 24-3M12	580	0.5	ATWB 24-3M12-Z	290	1.1
ATWB 24-4K12	580	0.6	ATWB 24-4K12-Z	290	1.3
ATWB 24-4L12	580	0.6	ATWB 24-4L12-Z	290	1.3
ATWB 24-4M12	580	0.6	ATWB 24-4M12-Z	290	1.3
ATWB 24-4N12	580	0.6	ATWB 24-4N12-Z	290	1.3
ATWB 24-5K12	580	0.7	ATWB 24-5K12-Z	290	1.6
ATWB 24-5L12	580	0.7	ATWB 24-5L12-Z	290	1.6
ATWB 24-5M12	580	0.7	ATWB 24-5M12-Z	290	1.6
ATWB 24-5N12	580	0.7	ATWB 24-5N12-Z	290	1.6
ATWB 24-6L12	580	0.9	ATWB 24-6L12-Z	290	1.8
ATWB 24-6M12	580	0.9	ATWB 24-6M12-Z	290	1.8
ATWB 24-6N12	580	0.9	ATWB 24-6N12-Z	290	1.8
ATWB 24-7L12	580	1.0	ATWB 24-7L12-Z	290	2.1
ATWB 24-7M12	580	1.0	ATWB 24-7M12-Z	290	2.1
ATWB 24-7N12	580	1.0	ATWB 24-7N12-Z	290	2.1
ATWB 24-3K14	580	0.5	ATWB 24-3K14-Z	290	1.1
ATWB 24-3L14	580	0.5	ATWB 24-3L14-Z	290	1.1
ATWB 24-3M14	580	0.5	ATWB 24-3M14-Z	290	1.1
ATWB 24-3N14	580	0.5	ATWB 24-3N14-Z	290	1.1
ATWB 24-4K14	580	0.7	ATWB 24-4K14-Z	290	1.4
ATWB 24-4L14	580	0.7	ATWB 24-4L14-Z	290	1.4
ATWB 24-4M14	580	0.7	ATWB 24-4M14-Z	290	1.4
ATWB 24-4N14	580	0.7	ATWB 24-4N14-Z	290	1.4
ATWB 24-5L14	580	0.8	ATWB 24-5L14-Z	290	1.7
ATWB 24-5M14	580	0.8	ATWB 24-5M14-Z	290	1.7

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 24-5N14	580	0.8	ATWB 24-5N14-Z	290	1.7
ATWB 24-6L14	580	0.9	ATWB 24-6L14-Z	290	2.0
ATWB 24-6M14	580	0.9	ATWB 24-6M14-Z	290	2.0
ATWB 24-6N14	580	0.9	ATWB 24-6N14-Z	290	2.0
ATWB 24-7L14	580	1.1	ATWB 24-7L14-Z	290	2.2
ATWB 24-7M14	580	1.1	ATWB 24-7M14-Z	290	2.2
ATWB 24-7N14	580	1.1	ATWB 24-7N14-Z	290	2.2
ATWB 24-3K18	580	0.6	ATWB 24-3K18-Z	290	1.3
ATWB 24-3L18	580	0.6	ATWB 24-3L18-Z	290	1.3
ATWB 24-3M18	580	0.6	ATWB 24-3M18-Z	290	1.3
ATWB 24-3N18	580	0.6	ATWB 24-3N18-Z	290	1.3
ATWB 24-4K18	580	0.8	ATWB 24-4K18-Z	290	1.6
ATWB 24-4L18	580	0.8	ATWB 24-4L18-Z	290	1.6
ATWB 24-4M18	580	0.8	ATWB 24-4M18-Z	290	1.6
ATWB 24-4N18	580	0.8	ATWB 24-4N18-Z	290	1.6
ATWB 24-4O18	580	0.8	ATWB 24-4O18-Z	290	1.6
ATWB 24-5L18	580	0.9	ATWB 24-5L18-Z	290	1.9
ATWB 24-5M18	580	0.9	ATWB 24-5M18-Z	290	1.9
ATWB 24-5N18	580	0.9	ATWB 24-5N18-Z	290	1.9
ATWB 24-5O18	580	0.9	ATWB 24-5O18-Z	290	1.9
ATWB 24-6M18	580	1.1	ATWB 24-6M18-Z	290	2.3
ATWB 24-6N18	580	1.1	ATWB 24-6N18-Z	290	2.3
ATWB 24-6O18	580	1.1	ATWB 24-6O18-Z	290	2.3
ATWB 24-6P18	580	1.1	ATWB 24-6P18-Z	290	2.3
ATWB 24-7M18	580	1.2	ATWB 24-7M18-Z	290	2.6
ATWB 24-7N18	580	1.2	ATWB 24-7N18-Z	290	2.6
ATWB 24-7O18	580	1.2	ATWB 24-7O18-Z	290	2.6
ATWB 24-7P18	580	1.2	ATWB 24-7P18-Z	290	2.6
ATWB 24-3L20	580	0.6	ATWB 24-3L20-Z	290	1.4
ATWB 24-3M20	580	0.6	ATWB 24-3M20-Z	290	1.4
ATWB 24-3N20	580	0.6	ATWB 24-3N20-Z	290	1.4
ATWB 24-3O20	580	0.6	ATWB 24-3O20-Z	290	1.4
ATWB 24-4L20	580	0.8	ATWB 24-4L20-Z	290	1.7
ATWB 24-4M20	580	0.8	ATWB 24-4M20-Z	290	1.7
ATWB 24-4N20	580	0.8	ATWB 24-4N20-Z	290	1.7
ATWB 24-4O20	580	0.8	ATWB 24-4O20-Z	290	1.7
ATWB 24-5M20	580	1.0	ATWB 24-5M20-Z	290	2.0
ATWB 24-5N20	580	1.0	ATWB 24-5N20-Z	290	2.0
ATWB 24-5O20	580	1.0	ATWB 24-5O20-Z	290	2.0
ATWB 24-5P20	580	1.0	ATWB 24-5P20-Z	290	2.0
ATWB 24-6N20	580	1.1	ATWB 24-6N20-Z	290	2.4
ATWB 24-6O20	580	1.1	ATWB 24-6O20-Z	290	2.4
ATWB 24-6P20	580	1.1	ATWB 24-6P20-Z	290	2.4
ATWB 24-7N20	580	1.3	ATWB 24-7N20-Z	290	2.7
ATWB 24-7O20	580	1.3	ATWB 24-7O20-Z	290	2.7
ATWB 24-7P20	580	1.3	ATWB 24-7P20-Z	290	2.7
ATWB 24-3J24	580	0.1	ATWB 24-3J24-Z	290	0.3
ATWB 24-3K24	580	0.1	ATWB 24-3K24-Z	290	0.3
ATWB 24-3L24	580	0.1	ATWB 24-3L24-Z	290	0.3
ATWB 24-3M24	580	0.1	ATWB 24-3M24-Z	290	0.3
ATWB 24-4J24	580	0.2	ATWB 24-4J24-Z	290	0.4
ATWB 24-4K24	580	0.2	ATWB 24-4K24-Z	290	0.4
ATWB 24-4L24	580	0.2	ATWB 24-4L24-Z	290	0.4
ATWB 24-4M24	580	0.2	ATWB 24-4M24-Z	290	0.4

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 24-4N24	580	0.2	ATWB 24-4N24-Z	290	0.4
ATWB 24-5K24	580	0.2	ATWB 24-5K24-Z	290	0.4
ATWB 24-5L24	580	0.2	ATWB 24-5L24-Z	290	0.4
ATWB 24-5M24	580	0.2	ATWB 24-5M24-Z	290	0.4
ATWB 24-5N24	580	0.2	ATWB 24-5N24-Z	290	0.4
ATWB 24-6L24	580	0.2	ATWB 24-6L24-Z	290	0.5
ATWB 24-6M24	580	0.2	ATWB 24-6M24-Z	290	0.5
ATWB 24-6N24	580	0.2	ATWB 24-6N24-Z	290	0.5
ATWB 24-7L24	580	0.3	ATWB 24-7L24-Z	290	0.6
ATWB 24-7M24	580	0.3	ATWB 24-7M24-Z	290	0.6
ATWB 24-7N24	580	0.3	ATWB 24-7N24-Z	290	0.6
ATWB 24-3K28	580	0.2	ATWB 24-3K28-Z	290	0.3
ATWB 24-3L28	580	0.2	ATWB 24-3L28-Z	290	0.3
ATWB 24-3M28	580	0.2	ATWB 24-3M28-Z	290	0.3
ATWB 24-3N28	580	0.2	ATWB 24-3N28-Z	290	0.3
ATWB 24-4K28	580	0.2	ATWB 24-4K28-Z	290	0.4
ATWB 24-4L28	580	0.2	ATWB 24-4L28-Z	290	0.4
ATWB 24-4M28	580	0.2	ATWB 24-4M28-Z	290	0.4
ATWB 24-4N28	580	0.2	ATWB 24-4N28-Z	290	0.4
ATWB 24-5L28	580	0.2	ATWB 24-5L28-Z	290	0.5
ATWB 24-5M28	580	0.2	ATWB 24-5M28-Z	290	0.5
ATWB 24-5N28	580	0.2	ATWB 24-5N28-Z	290	0.5
ATWB 24-6L28	580	0.3	ATWB 24-6L28-Z	290	0.6
ATWB 24-6M28	580	0.3	ATWB 24-6M28-Z	290	0.6
ATWB 24-6N28	580	0.3	ATWB 24-6N28-Z	290	0.6
ATWB 24-7L28	580	0.3	ATWB 24-7L28-Z	290	0.6
ATWB 24-7M28	580	0.3	ATWB 24-7M28-Z	290	0.6
ATWB 24-7N28	580	0.3	ATWB 24-7N28-Z	290	0.6
ATWB 24-3K36	580	0.2	ATWB 24-3K36-Z	290	0.4
ATWB 24-3L36	580	0.2	ATWB 24-3L36-Z	290	0.4
ATWB 24-3M36	580	0.2	ATWB 24-3M36-Z	290	0.4
ATWB 24-3N36	580	0.2	ATWB 24-3N36-Z	290	0.4
ATWB 24-4K36	580	0.2	ATWB 24-4K36-Z	290	0.5
ATWB 24-4L36	580	0.2	ATWB 24-4L36-Z	290	0.5
ATWB 24-4M36	580	0.2	ATWB 24-4M36-Z	290	0.5
ATWB 24-4N36	580	0.2	ATWB 24-4N36-Z	290	0.5
ATWB 24-5L36	580	0.3	ATWB 24-5L36-Z	290	0.6
ATWB 24-5M36	580	0.3	ATWB 24-5M36-Z	290	0.6
ATWB 24-5N36	580	0.3	ATWB 24-5N36-Z	290	0.6
ATWB 24-5O36	580	0.3	ATWB 24-5O36-Z	290	0.6
ATWB 24-6M36	580	0.3	ATWB 24-6M36-Z	290	0.6
ATWB 24-6N36	580	0.3	ATWB 24-6N36-Z	290	0.6
ATWB 24-6O36	580	0.3	ATWB 24-6O36-Z	290	0.6
ATWB 24-6P36	580	0.3	ATWB 24-6P36-Z	290	0.6
ATWB 24-7M36	580	0.4	ATWB 24-7M36-Z	290	0.7
ATWB 24-7N36	580	0.4	ATWB 24-7N36-Z	290	0.7
ATWB 24-7O36	580	0.4	ATWB 24-7O36-Z	290	0.7
ATWB 24-7P36	580	0.4	ATWB 24-7P36-Z	290	0.7
ATWB 24-3L40	580	0.2	ATWB 24-3L40-Z	290	0.4
ATWB 24-3M40	580	0.2	ATWB 24-3M40-Z	290	0.4
ATWB 24-3N40	580	0.2	ATWB 24-3N40-Z	290	0.4
ATWB 24-3O40	580	0.2	ATWB 24-3O40-Z	290	0.4
ATWB 24-4L40	580	0.2	ATWB 24-4L40-Z	290	0.5
ATWB 24-4M40	580	0.2	ATWB 24-4M40-Z	290	0.5

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 24-4N40	580	0.2	ATWB 24-4N40-Z	290	0.5
ATWB 24-4O40	580	0.2	ATWB 24-4O40-Z	290	0.5
ATWB 24-5M40	580	0.3	ATWB 24-5M40-Z	290	0.6
ATWB 24-5N40	580	0.3	ATWB 24-5N40-Z	290	0.6
ATWB 24-5O40	580	0.3	ATWB 24-5O40-Z	290	0.6
ATWB 24-5P40	580	0.3	ATWB 24-5P40-Z	290	0.6
ATWB 24-6N40	580	0.3	ATWB 24-6N40-Z	290	0.7
ATWB 24-6O40	580	0.3	ATWB 24-6O40-Z	290	0.7
ATWB 24-6P40	580	0.3	ATWB 24-6P40-Z	290	0.7
ATWB 24-7N40	580	0.4	ATWB 24-7N40-Z	290	0.8
ATWB 24-7O40	580	0.4	ATWB 24-7O40-Z	290	0.8
ATWB 24-7P40	580	0.4	ATWB 24-7P40-Z	290	0.8
ATWB 8-3G9	370	1.3	ATWB 8-3G9-Z	185	2.7
ATWB 8-3H9	370	1.3	ATWB 8-3H9-Z	185	2.7
ATWB 8-3I9	370	1.3	ATWB 8-3I9-Z	185	2.7
ATWB 8-3J9	370	1.3	ATWB 8-3J9-Z	185	2.7
ATWB 8-4G9	370	1.6	ATWB 8-4G9-Z	185	3.4
ATWB 8-4H9	370	1.6	ATWB 8-4H9-Z	185	3.4
ATWB 8-4I9	370	1.6	ATWB 8-4I9-Z	185	3.4
ATWB 8-4J9	370	1.6	ATWB 8-4J9-Z	185	3.4
ATWB 8-4K9	370	1.6	ATWB 8-4K9-Z	185	3.4
ATWB 8-5G9	370	2.0	ATWB 8-5G9-Z	185	4.2
ATWB 8-5H9	370	2.0	ATWB 8-5H9-Z	185	4.2
ATWB 8-5I9	370	2.0	ATWB 8-5I9-Z	185	4.2
ATWB 8-5J9	370	2.0	ATWB 8-5J9-Z	185	4.2
ATWB 8-5K9	370	2.0	ATWB 8-5K9-Z	185	4.2
ATWB 8-6G9	370	2.4	ATWB 8-6G9-Z	185	4.9
ATWB 8-6H9	370	2.4	ATWB 8-6H9-Z	185	4.9
ATWB 8-6I9	370	2.4	ATWB 8-6I9-Z	185	4.9
ATWB 8-6J9	370	2.4	ATWB 8-6J9-Z	185	4.9
ATWB 8-6K9	370	2.4	ATWB 8-6K9-Z	185	4.9
ATWB 8-7G9	370	2.7	ATWB 8-7G9-Z	185	5.7
ATWB 8-7H9	370	2.7	ATWB 8-7H9-Z	185	5.7
ATWB 8-7I9	370	2.7	ATWB 8-7I9-Z	185	5.7
ATWB 8-7J9	370	2.7	ATWB 8-7J9-Z	185	5.7
ATWB 8-7K9	370	2.7	ATWB 8-7K9-Z	185	5.7
ATWB 8-3H11	370	1.4	ATWB 8-3H11-Z	185	2.9
ATWB 8-3I11	370	1.4	ATWB 8-3I11-Z	185	2.9
ATWB 8-3J11	370	1.4	ATWB 8-3J11-Z	185	2.9
ATWB 8-3K11	370	1.4	ATWB 8-3K11-Z	185	2.9
ATWB 8-4H11	370	1.8	ATWB 8-4H11-Z	185	3.7
ATWB 8-4I11	370	1.8	ATWB 8-4I11-Z	185	3.7
ATWB 8-4J11	370	1.8	ATWB 8-4J11-Z	185	3.7
ATWB 8-4K11	370	1.8	ATWB 8-4K11-Z	185	3.7
ATWB 8-5H11	370	2.1	ATWB 8-5H11-Z	185	4.5
ATWB 8-5I11	370	2.1	ATWB 8-5I11-Z	185	4.5
ATWB 8-5J11	370	2.1	ATWB 8-5J11-Z	185	4.5
ATWB 8-5K11	370	2.1	ATWB 8-5K11-Z	185	4.5
ATWB 8-6H11	370	2.5	ATWB 8-6H11-Z	185	5.3
ATWB 8-6I11	370	2.5	ATWB 8-6I11-Z	185	5.3
ATWB 8-6J11	370	2.5	ATWB 8-6J11-Z	185	5.3
ATWB 8-6K11	370	2.5	ATWB 8-6K11-Z	185	5.3
ATWB 8-7H11	370	2.9	ATWB 8-7H11-Z	185	6.1
ATWB 8-7I11	370	2.9	ATWB 8-7I11-Z	185	6.1

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 8-7J11	370	2.9	ATWB 8-7J11-Z	185	6.1
ATWB 8-7K11	370	2.9	ATWB 8-7K11-Z	185	6.1
ATWB 8-3H12	370	1.5	ATWB 8-3H12-Z	185	3.1
ATWB 8-3I12	370	1.5	ATWB 8-3I12-Z	185	3.1
ATWB 8-3J12	370	1.5	ATWB 8-3J12-Z	185	3.1
ATWB 8-3K12	370	1.5	ATWB 8-3K12-Z	185	3.1
ATWB 8-4H12	370	1.9	ATWB 8-4H12-Z	185	3.9
ATWB 8-4I12	370	1.9	ATWB 8-4I12-Z	185	3.9
ATWB 8-4J12	370	1.9	ATWB 8-4J12-Z	185	3.9
ATWB 8-4K12	370	1.9	ATWB 8-4K12-Z	185	3.9
ATWB 8-4L12	370	1.9	ATWB 8-4L12-Z	185	3.9
ATWB 8-5H12	370	2.3	ATWB 8-5H12-Z	185	4.8
ATWB 8-5I12	370	2.3	ATWB 8-5I12-Z	185	4.8
ATWB 8-5J12	370	2.3	ATWB 8-5J12-Z	185	4.8
ATWB 8-5K12	370	2.3	ATWB 8-5K12-Z	185	4.8
ATWB 8-5L12	370	2.3	ATWB 8-5L12-Z	185	4.8
ATWB 8-6H12	370	2.7	ATWB 8-6H12-Z	185	5.7
ATWB 8-6I12	370	2.7	ATWB 8-6I12-Z	185	5.7
ATWB 8-6J12	370	2.7	ATWB 8-6J12-Z	185	5.7
ATWB 8-6K12	370	2.7	ATWB 8-6K12-Z	185	5.7
ATWB 8-6L12	370	2.7	ATWB 8-6L12-Z	185	5.7
ATWB 8-7H12	370	3.1	ATWB 8-7H12-Z	185	6.6
ATWB 8-7I12	370	3.1	ATWB 8-7I12-Z	185	6.6
ATWB 8-7J12	370	3.1	ATWB 8-7J12-Z	185	6.6
ATWB 8-7K12	370	3.1	ATWB 8-7K12-Z	185	6.6
ATWB 8-7L12	370	3.1	ATWB 8-7L12-Z	185	6.6
ATWB 8-3I14	370	1.6	ATWB 8-3I14-Z	185	3.3
ATWB 8-3J14	370	1.6	ATWB 8-3J14-Z	185	3.3
ATWB 8-3K14	370	1.6	ATWB 8-3K14-Z	185	3.3
ATWB 8-3L14	370	1.6	ATWB 8-3L14-Z	185	3.3
ATWB 8-4I14	370	2.0	ATWB 8-4I14-Z	185	4.3
ATWB 8-4J14	370	2.0	ATWB 8-4J14-Z	185	4.3
ATWB 8-4K14	370	2.0	ATWB 8-4K14-Z	185	4.3
ATWB 8-4L14	370	2.0	ATWB 8-4L14-Z	185	4.3
ATWB 8-4M14	370	2.0	ATWB 8-4M14-Z	185	4.3
ATWB 8-5I14	370	2.5	ATWB 8-5I14-Z	185	5.2
ATWB 8-5J14	370	2.5	ATWB 8-5J14-Z	185	5.2
ATWB 8-5K14	370	2.5	ATWB 8-5K14-Z	185	5.2
ATWB 8-5L14	370	2.5	ATWB 8-5L14-Z	185	5.2
ATWB 8-5M14	370	2.5	ATWB 8-5M14-Z	185	5.2
ATWB 8-6I14	370	3.0	ATWB 8-6I14-Z	185	6.2
ATWB 8-6J14	370	3.0	ATWB 8-6J14-Z	185	6.2
ATWB 8-6K14	370	3.0	ATWB 8-6K14-Z	185	6.2
ATWB 8-6L14	370	3.0	ATWB 8-6L14-Z	185	6.2
ATWB 8-6M14	370	3.0	ATWB 8-6M14-Z	185	6.2
ATWB 8-7I14	370	3.4	ATWB 8-7I14-Z	185	7.2
ATWB 8-7J14	370	3.4	ATWB 8-7J14-Z	185	7.2
ATWB 8-7K14	370	3.4	ATWB 8-7K14-Z	185	7.2
ATWB 8-7L14	370	3.4	ATWB 8-7L14-Z	185	7.2
ATWB 8-7M14	370	3.4	ATWB 8-7M14-Z	185	7.2
ATWB 8-3G18	370	1.8	ATWB 8-3G18-Z	185	3.8
ATWB 8-3H18	370	1.8	ATWB 8-3H18-Z	185	3.8
ATWB 8-3I18	370	1.8	ATWB 8-3I18-Z	185	3.8
ATWB 8-3J18	370	1.8	ATWB 8-3J18-Z	185	3.8

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 8-4G18	370	2.4	ATWB 8-4G18-Z	185	5.0
ATWB 8-4H18	370	2.4	ATWB 8-4H18-Z	185	5.0
ATWB 8-4I18	370	2.4	ATWB 8-4I18-Z	185	5.0
ATWB 8-4J18	370	2.4	ATWB 8-4J18-Z	185	5.0
ATWB 8-4K18	370	2.4	ATWB 8-4K18-Z	185	5.0
ATWB 8-5G18	370	2.9	ATWB 8-5G18-Z	185	6.1
ATWB 8-5H18	370	2.9	ATWB 8-5H18-Z	185	6.1
ATWB 8-5I18	370	2.9	ATWB 8-5I18-Z	185	6.1
ATWB 8-5J18	370	2.9	ATWB 8-5J18-Z	185	6.1
ATWB 8-5K18	370	2.9	ATWB 8-5K18-Z	185	6.1
ATWB 8-6G18	370	3.4	ATWB 8-6G18-Z	185	7.2
ATWB 8-6H18	370	3.4	ATWB 8-6H18-Z	185	7.2
ATWB 8-6I18	370	3.4	ATWB 8-6I18-Z	185	7.2
ATWB 8-6J18	370	3.4	ATWB 8-6J18-Z	185	7.2
ATWB 8-6K18	370	3.4	ATWB 8-6K18-Z	185	7.2
ATWB 8-7G18	370	4.0	ATWB 8-7G18-Z	185	8.3
ATWB 8-7H18	370	4.0	ATWB 8-7H18-Z	185	8.3
ATWB 8-7I18	370	4.0	ATWB 8-7I18-Z	185	8.3
ATWB 8-7J18	370	4.0	ATWB 8-7J18-Z	185	8.3
ATWB 8-7K18	370	4.0	ATWB 8-7K18-Z	185	8.3
ATWB 8-3H21	370	2.0	ATWB 8-3H21-Z	185	4.2
ATWB 8-3I21	370	2.0	ATWB 8-3I21-Z	185	4.2
ATWB 8-3J21	370	2.0	ATWB 8-3J21-Z	185	4.2
ATWB 8-3K21	370	2.0	ATWB 8-3K21-Z	185	4.2
ATWB 8-4H21	370	2.6	ATWB 8-4H21-Z	185	5.5
ATWB 8-4I21	370	2.6	ATWB 8-4I21-Z	185	5.5
ATWB 8-4J21	370	2.6	ATWB 8-4J21-Z	185	5.5
ATWB 8-4K21	370	2.6	ATWB 8-4K21-Z	185	5.5
ATWB 8-5H21	370	3.2	ATWB 8-5H21-Z	185	6.7
ATWB 8-5I21	370	3.2	ATWB 8-5I21-Z	185	6.7
ATWB 8-5J21	370	3.2	ATWB 8-5J21-Z	185	6.7
ATWB 8-5K21	370	3.2	ATWB 8-5K21-Z	185	6.7
ATWB 8-6H21	370	3.8	ATWB 8-6H21-Z	185	8.0
ATWB 8-6I21	370	3.8	ATWB 8-6I21-Z	185	8.0
ATWB 8-6J21	370	3.8	ATWB 8-6J21-Z	185	8.0
ATWB 8-6K21	370	3.8	ATWB 8-6K21-Z	185	8.0
ATWB 8-7H21	370	4.4	ATWB 8-7H21-Z	185	9.2
ATWB 8-7I21	370	4.4	ATWB 8-7I21-Z	185	9.2
ATWB 8-7J21	370	4.4	ATWB 8-7J21-Z	185	9.2
ATWB 8-7K21	370	4.4	ATWB 8-7K21-Z	185	9.2
ATWB 8-3H24	370	0.4	ATWB 8-3H24-Z	185	0.9
ATWB 8-3I24	370	0.4	ATWB 8-3I24-Z	185	0.9
ATWB 8-3J24	370	0.4	ATWB 8-3J24-Z	185	0.9
ATWB 8-3K24	370	0.4	ATWB 8-3K24-Z	185	0.9
ATWB 8-4H24	370	0.5	ATWB 8-4H24-Z	185	1.1
ATWB 8-4I24	370	0.5	ATWB 8-4I24-Z	185	1.1
ATWB 8-4J24	370	0.5	ATWB 8-4J24-Z	185	1.1
ATWB 8-4K24	370	0.5	ATWB 8-4K24-Z	185	1.1
ATWB 8-4L24	370	0.5	ATWB 8-4L24-Z	185	1.1
ATWB 8-5H24	370	0.7	ATWB 8-5H24-Z	185	1.4
ATWB 8-5I24	370	0.7	ATWB 8-5I24-Z	185	1.4
ATWB 8-5J24	370	0.7	ATWB 8-5J24-Z	185	1.4
ATWB 8-5K24	370	0.7	ATWB 8-5K24-Z	185	1.4
ATWB 8-5L24	370	0.7	ATWB 8-5L24-Z	185	1.4

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 8-6H24	370	0.8	ATWB 8-6H24-Z	185	1.6
ATWB 8-6I24	370	0.8	ATWB 8-6I24-Z	185	1.6
ATWB 8-6J24	370	0.8	ATWB 8-6J24-Z	185	1.6
ATWB 8-6K24	370	0.8	ATWB 8-6K24-Z	185	1.6
ATWB 8-6L24	370	0.8	ATWB 8-6L24-Z	185	1.6
ATWB 8-7H24	370	0.9	ATWB 8-7H24-Z	185	1.9
ATWB 8-7I24	370	0.9	ATWB 8-7I24-Z	185	1.9
ATWB 8-7J24	370	0.9	ATWB 8-7J24-Z	185	1.9
ATWB 8-7K24	370	0.9	ATWB 8-7K24-Z	185	1.9
ATWB 8-7L24	370	0.9	ATWB 8-7L24-Z	185	1.9
ATWB 8-3I28	370	0.5	ATWB 8-3I28-Z	185	1.0
ATWB 8-3J28	370	0.5	ATWB 8-3J28-Z	185	1.0
ATWB 8-3K28	370	0.5	ATWB 8-3K28-Z	185	1.0
ATWB 8-3L28	370	0.5	ATWB 8-3L28-Z	185	1.0
ATWB 8-4I28	370	0.6	ATWB 8-4I28-Z	185	1.2
ATWB 8-4J28	370	0.6	ATWB 8-4J28-Z	185	1.2
ATWB 8-4K28	370	0.6	ATWB 8-4K28-Z	185	1.2
ATWB 8-4L28	370	0.6	ATWB 8-4L28-Z	185	1.2
ATWB 8-4M28	370	0.6	ATWB 8-4M28-Z	185	1.2
ATWB 8-5I28	370	0.7	ATWB 8-5I28-Z	185	1.5
ATWB 8-5J28	370	0.7	ATWB 8-5J28-Z	185	1.5
ATWB 8-5K28	370	0.7	ATWB 8-5K28-Z	185	1.5
ATWB 8-5L28	370	0.7	ATWB 8-5L28-Z	185	1.5
ATWB 8-5M28	370	0.7	ATWB 8-5M28-Z	185	1.5
ATWB 8-6I28	370	0.8	ATWB 8-6I28-Z	185	1.8
ATWB 8-6J28	370	0.8	ATWB 8-6J28-Z	185	1.8
ATWB 8-6K28	370	0.8	ATWB 8-6K28-Z	185	1.8
ATWB 8-6L28	370	0.8	ATWB 8-6L28-Z	185	1.8
ATWB 8-6M28	370	0.8	ATWB 8-6M28-Z	185	1.8
ATWB 8-7I28	370	1.0	ATWB 8-7I28-Z	185	2.1
ATWB 8-7J28	370	1.0	ATWB 8-7J28-Z	185	2.1
ATWB 8-7K28	370	1.0	ATWB 8-7K28-Z	185	2.1
ATWB 8-7L28	370	1.0	ATWB 8-7L28-Z	185	2.1
ATWB 8-7M28	370	1.0	ATWB 8-7M28-Z	185	2.1
ATWB 8-3H36	370	0.5	ATWB 8-3H36-Z	185	1.1
ATWB 8-3I36	370	0.5	ATWB 8-3I36-Z	185	1.1
ATWB 8-3J36	370	0.5	ATWB 8-3J36-Z	185	1.1
ATWB 8-4H36	370	0.7	ATWB 8-4H36-Z	185	1.4
ATWB 8-4I36	370	0.7	ATWB 8-4I36-Z	185	1.4
ATWB 8-4J36	370	0.7	ATWB 8-4J36-Z	185	1.4
ATWB 8-4K36	370	0.7	ATWB 8-4K36-Z	185	1.4
ATWB 8-5H36	370	0.8	ATWB 8-5H36-Z	185	1.7
ATWB 8-5I36	370	0.8	ATWB 8-5I36-Z	185	1.7
ATWB 8-5J36	370	0.8	ATWB 8-5J36-Z	185	1.7
ATWB 8-5K36	370	0.8	ATWB 8-5K36-Z	185	1.7
ATWB 8-6H36	370	1.0	ATWB 8-6H36-Z	185	2.1
ATWB 8-6I36	370	1.0	ATWB 8-6I36-Z	185	2.1
ATWB 8-6J36	370	1.0	ATWB 8-6J36-Z	185	2.1
ATWB 8-6K36	370	1.0	ATWB 8-6K36-Z	185	2.1
ATWB 8-6L36	370	1.0	ATWB 8-6L36-Z	185	2.1
ATWB 8-7H36	370	1.1	ATWB 8-7H36-Z	185	2.4
ATWB 8-7I36	370	1.1	ATWB 8-7I36-Z	185	2.4
ATWB 8-7J36	370	1.1	ATWB 8-7J36-Z	185	2.4
ATWB 8-7K36	370	1.1	ATWB 8-7K36-Z	185	2.4

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 8-7L36	370	1.1	ATWB 8-7L36-Z	185	2.4
ATWB 8-3H42	370	0.6	ATWB 8-3H42-Z	185	1.2
ATWB 8-3I42	370	0.6	ATWB 8-3I42-Z	185	1.2
ATWB 8-3J42	370	0.6	ATWB 8-3J42-Z	185	1.2
ATWB 8-3K42	370	0.6	ATWB 8-3K42-Z	185	1.2
ATWB 8-4H42	370	0.7	ATWB 8-4H42-Z	185	1.6
ATWB 8-4I42	370	0.7	ATWB 8-4I42-Z	185	1.6
ATWB 8-4J42	370	0.7	ATWB 8-4J42-Z	185	1.6
ATWB 8-4K42	370	0.7	ATWB 8-4K42-Z	185	1.6
ATWB 8-5H42	370	0.9	ATWB 8-5H42-Z	185	1.9
ATWB 8-5I42	370	0.9	ATWB 8-5I42-Z	185	1.9
ATWB 8-5J42	370	0.9	ATWB 8-5J42-Z	185	1.9
ATWB 8-5K42	370	0.9	ATWB 8-5K42-Z	185	1.9
ATWB 8-5L42	370	0.9	ATWB 8-5L42-Z	185	1.9
ATWB 8-6H42	370	1.1	ATWB 8-6H42-Z	185	2.3
ATWB 8-6I42	370	1.1	ATWB 8-6I42-Z	185	2.3
ATWB 8-6J42	370	1.1	ATWB 8-6J42-Z	185	2.3
ATWB 8-6K42	370	1.1	ATWB 8-6K42-Z	185	2.3
ATWB 8-6L42	370	1.1	ATWB 8-6L42-Z	185	2.3
ATWB 8-7H42	370	1.3	ATWB 8-7H42-Z	185	2.6
ATWB 8-7I42	370	1.3	ATWB 8-7I42-Z	185	2.6
ATWB 8-7J42	370	1.3	ATWB 8-7J42-Z	185	2.6
ATWB 8-7K42	370	1.3	ATWB 8-7K42-Z	185	2.6
ATWB 8-7L42	370	1.3	ATWB 8-7L42-Z	185	2.6
ATWB 16-3H11	370	0.4	ATWB 16-3H11-Z	185	0.8
ATWB 16-3I11	370	0.4	ATWB 16-3I11-Z	185	0.8
ATWB 16-3J11	370	0.4	ATWB 16-3J11-Z	185	0.8
ATWB 16-3K11	370	0.4	ATWB 16-3K11-Z	185	0.8
ATWB 16-4H11	370	0.5	ATWB 16-4H11-Z	185	1.1
ATWB 16-4I11	370	0.5	ATWB 16-4I11-Z	185	1.1
ATWB 16-4J11	370	0.5	ATWB 16-4J11-Z	185	1.1
ATWB 16-4K11	370	0.5	ATWB 16-4K11-Z	185	1.1
ATWB 16-5H11	370	0.6	ATWB 16-5H11-Z	185	1.3
ATWB 16-5I11	370	0.6	ATWB 16-5I11-Z	185	1.3
ATWB 16-5J11	370	0.6	ATWB 16-5J11-Z	185	1.3
ATWB 16-5K11	370	0.6	ATWB 16-5K11-Z	185	1.3
ATWB 16-6H11	370	0.7	ATWB 16-6H11-Z	185	1.5
ATWB 16-6I11	370	0.7	ATWB 16-6I11-Z	185	1.5
ATWB 16-6J11	370	0.7	ATWB 16-6J11-Z	185	1.5
ATWB 16-6K11	370	0.7	ATWB 16-6K11-Z	185	1.5
ATWB 16-7H11	370	0.8	ATWB 16-7H11-Z	185	1.8
ATWB 16-7I11	370	0.8	ATWB 16-7I11-Z	185	1.8
ATWB 16-7J11	370	0.8	ATWB 16-7J11-Z	185	1.8
ATWB 16-7K11	370	0.8	ATWB 16-7K11-Z	185	1.8
ATWB 16-3H12	370	0.4	ATWB 16-3H12-Z	185	0.9
ATWB 16-3I12	370	0.4	ATWB 16-3I12-Z	185	0.9
ATWB 16-3J12	370	0.4	ATWB 16-3J12-Z	185	0.9
ATWB 16-3K12	370	0.4	ATWB 16-3K12-Z	185	0.9
ATWB 16-4H12	370	0.5	ATWB 16-4H12-Z	185	1.1
ATWB 16-4I12	370	0.5	ATWB 16-4I12-Z	185	1.1
ATWB 16-4J12	370	0.5	ATWB 16-4J12-Z	185	1.1
ATWB 16-4K12	370	0.5	ATWB 16-4K12-Z	185	1.1
ATWB 16-4L12	370	0.5	ATWB 16-4L12-Z	185	1.1
ATWB 16-5H12	370	0.7	ATWB 16-5H12-Z	185	1.4

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 16-5I12	370	0.7	ATWB 16-5I12-Z	185	1.4
ATWB 16-5J12	370	0.7	ATWB 16-5J12-Z	185	1.4
ATWB 16-5K12	370	0.7	ATWB 16-5K12-Z	185	1.4
ATWB 16-5L12	370	0.7	ATWB 16-5L12-Z	185	1.4
ATWB 16-6H12	370	0.8	ATWB 16-6H12-Z	185	1.6
ATWB 16-6I12	370	0.8	ATWB 16-6I12-Z	185	1.6
ATWB 16-6J12	370	0.8	ATWB 16-6J12-Z	185	1.6
ATWB 16-6K12	370	0.8	ATWB 16-6K12-Z	185	1.6
ATWB 16-6L12	370	0.8	ATWB 16-6L12-Z	185	1.6
ATWB 16-7H12	370	0.9	ATWB 16-7H12-Z	185	1.9
ATWB 16-7I12	370	0.9	ATWB 16-7I12-Z	185	1.9
ATWB 16-7J12	370	0.9	ATWB 16-7J12-Z	185	1.9
ATWB 16-7K12	370	0.9	ATWB 16-7K12-Z	185	1.9
ATWB 16-7L12	370	0.9	ATWB 16-7L12-Z	185	1.9
ATWB 16-3I14	370	0.5	ATWB 16-3I14-Z	185	1.0
ATWB 16-3J14	370	0.5	ATWB 16-3J14-Z	185	1.0
ATWB 16-3K14	370	0.5	ATWB 16-3K14-Z	185	1.0
ATWB 16-3L14	370	0.5	ATWB 16-3L14-Z	185	1.0
ATWB 16-4I14	370	0.6	ATWB 16-4I14-Z	185	1.2
ATWB 16-4J14	370	0.6	ATWB 16-4J14-Z	185	1.2
ATWB 16-4K14	370	0.6	ATWB 16-4K14-Z	185	1.2
ATWB 16-4L14	370	0.6	ATWB 16-4L14-Z	185	1.2
ATWB 16-4M14	370	0.6	ATWB 16-4M14-Z	185	1.2
ATWB 16-5I14	370	0.7	ATWB 16-5I14-Z	185	1.5
ATWB 16-5J14	370	0.7	ATWB 16-5J14-Z	185	1.5
ATWB 16-5K14	370	0.7	ATWB 16-5K14-Z	185	1.5
ATWB 16-5L14	370	0.7	ATWB 16-5L14-Z	185	1.5
ATWB 16-5M14	370	0.7	ATWB 16-5M14-Z	185	1.5
ATWB 16-6I14	370	0.8	ATWB 16-6I14-Z	185	1.8
ATWB 16-6J14	370	0.8	ATWB 16-6J14-Z	185	1.8
ATWB 16-6K14	370	0.8	ATWB 16-6K14-Z	185	1.8
ATWB 16-6L14	370	0.8	ATWB 16-6L14-Z	185	1.8
ATWB 16-6M14	370	0.8	ATWB 16-6M14-Z	185	1.8
ATWB 16-7I14	370	1.0	ATWB 16-7I14-Z	185	2.1
ATWB 16-7J14	370	1.0	ATWB 16-7J14-Z	185	2.1
ATWB 16-7K14	370	1.0	ATWB 16-7K14-Z	185	2.1
ATWB 16-7L14	370	1.0	ATWB 16-7L14-Z	185	2.1
ATWB 16-7M14	370	1.0	ATWB 16-7M14-Z	185	2.1
ATWB 10-3I12	470	1.6	ATWB 10-3I12-Z	235	3.3
ATWB 10-3J12	470	1.6	ATWB 10-3J12-Z	235	3.3
ATWB 10-3K12	470	1.6	ATWB 10-3K12-Z	235	3.3
ATWB 10-3L12	470	1.6	ATWB 10-3L12-Z	235	3.3
ATWB 10-3M12	470	1.6	ATWB 10-3M12-Z	235	3.3
ATWB 10-4I12	470	2.0	ATWB 10-4I12-Z	235	4.2
ATWB 10-4J12	470	2.0	ATWB 10-4J12-Z	235	4.2
ATWB 10-4K12	470	2.0	ATWB 10-4K12-Z	235	4.2
ATWB 10-4L12	470	2.0	ATWB 10-4L12-Z	235	4.2
ATWB 10-4M12	470	2.0	ATWB 10-4M12-Z	235	4.2
ATWB 10-5I12	470	2.4	ATWB 10-5I12-Z	235	5.1
ATWB 10-5J12	470	2.4	ATWB 10-5J12-Z	235	5.1
ATWB 10-5K12	470	2.4	ATWB 10-5K12-Z	235	5.1
ATWB 10-5L12	470	2.4	ATWB 10-5L12-Z	235	5.1
ATWB 10-5M12	470	2.4	ATWB 10-5M12-Z	235	5.1
ATWB 10-6I12	470	2.8	ATWB 10-6I12-Z	235	6.0

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 10-6J12	470	2.8	ATWB 10-6J12-Z	235	6.0
ATWB 10-6K12	470	2.8	ATWB 10-6K12-Z	235	6.0
ATWB 10-6L12	470	2.8	ATWB 10-6L12-Z	235	6.0
ATWB 10-6M12	470	2.8	ATWB 10-6M12-Z	235	6.0
ATWB 10-7I12	470	3.3	ATWB 10-7I12-Z	235	6.8
ATWB 10-7J12	470	3.3	ATWB 10-7J12-Z	235	6.8
ATWB 10-7K12	470	3.3	ATWB 10-7K12-Z	235	6.8
ATWB 10-7L12	470	3.3	ATWB 10-7L12-Z	235	6.8
ATWB 10-7M12	470	3.3	ATWB 10-7M12-Z	235	6.8
ATWB 10-3I18	470	1.9	ATWB 10-3I18-Z	235	4.1
ATWB 10-3J18	470	1.9	ATWB 10-3J18-Z	235	4.1
ATWB 10-3K18	470	1.9	ATWB 10-3K18-Z	235	4.1
ATWB 10-3L18	470	1.9	ATWB 10-3L18-Z	235	4.1
ATWB 10-3M18	470	1.9	ATWB 10-3M18-Z	235	4.1
ATWB 10-3N18	470	1.9	ATWB 10-3N18-Z	235	4.1
ATWB 10-4I18	470	2.5	ATWB 10-4I18-Z	235	5.2
ATWB 10-4J18	470	2.5	ATWB 10-4J18-Z	235	5.2
ATWB 10-4K18	470	2.5	ATWB 10-4K18-Z	235	5.2
ATWB 10-4L18	470	2.5	ATWB 10-4L18-Z	235	5.2
ATWB 10-4M18	470	2.5	ATWB 10-4M18-Z	235	5.2
ATWB 10-4N18	470	2.5	ATWB 10-4N18-Z	235	5.2
ATWB 10-5I18	470	3.0	ATWB 10-5I18-Z	235	6.3
ATWB 10-5J18	470	3.0	ATWB 10-5J18-Z	235	6.3
ATWB 10-5K18	470	3.0	ATWB 10-5K18-Z	235	6.3
ATWB 10-5L18	470	3.0	ATWB 10-5L18-Z	235	6.3
ATWB 10-5M18	470	3.0	ATWB 10-5M18-Z	235	6.3
ATWB 10-5N18	470	3.0	ATWB 10-5N18-Z	235	6.3
ATWB 10-6I18	470	3.6	ATWB 10-6I18-Z	235	7.5
ATWB 10-6J18	470	3.6	ATWB 10-6J18-Z	235	7.5
ATWB 10-6K18	470	3.6	ATWB 10-6K18-Z	235	7.5
ATWB 10-6L18	470	3.6	ATWB 10-6L18-Z	235	7.5
ATWB 10-6M18	470	3.6	ATWB 10-6M18-Z	235	7.5
ATWB 10-6N18	470	3.6	ATWB 10-6N18-Z	235	7.5
ATWB 10-7I18	470	4.1	ATWB 10-7I18-Z	235	8.6
ATWB 10-7J18	470	4.1	ATWB 10-7J18-Z	235	8.6
ATWB 10-7K18	470	4.1	ATWB 10-7K18-Z	235	8.6
ATWB 10-7L18	470	4.1	ATWB 10-7L18-Z	235	8.6
ATWB 10-7M18	470	4.1	ATWB 10-7M18-Z	235	8.6
ATWB 10-7N18	470	4.1	ATWB 10-7N18-Z	235	8.6
ATWB 10-3I24	470	0.5	ATWB 10-3I24-Z	235	1.0
ATWB 10-3J24	470	0.5	ATWB 10-3J24-Z	235	1.0
ATWB 10-3K24	470	0.5	ATWB 10-3K24-Z	235	1.0
ATWB 10-3L24	470	0.5	ATWB 10-3L24-Z	235	1.0
ATWB 10-3M24	470	0.5	ATWB 10-3M24-Z	235	1.0
ATWB 10-4I24	470	0.6	ATWB 10-4I24-Z	235	1.2
ATWB 10-4J24	470	0.6	ATWB 10-4J24-Z	235	1.2
ATWB 10-4K24	470	0.6	ATWB 10-4K24-Z	235	1.2
ATWB 10-4L24	470	0.6	ATWB 10-4L24-Z	235	1.2
ATWB 10-4M24	470	0.6	ATWB 10-4M24-Z	235	1.2
ATWB 10-5I24	470	0.7	ATWB 10-5I24-Z	235	1.5
ATWB 10-5J24	470	0.7	ATWB 10-5J24-Z	235	1.5
ATWB 10-5K24	470	0.7	ATWB 10-5K24-Z	235	1.5
ATWB 10-5L24	470	0.7	ATWB 10-5L24-Z	235	1.5
ATWB 10-5M24	470	0.7	ATWB 10-5M24-Z	235	1.5

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 10-6I24	470	0.8	ATWB 10-6I24-Z	235	1.7
ATWB 10-6J24	470	0.8	ATWB 10-6J24-Z	235	1.7
ATWB 10-6K24	470	0.8	ATWB 10-6K24-Z	235	1.7
ATWB 10-6L24	470	0.8	ATWB 10-6L24-Z	235	1.7
ATWB 10-6M24	470	0.8	ATWB 10-6M24-Z	235	1.7
ATWB 10-7I24	470	0.9	ATWB 10-7I24-Z	235	2.0
ATWB 10-7J24	470	0.9	ATWB 10-7J24-Z	235	2.0
ATWB 10-7K24	470	0.9	ATWB 10-7K24-Z	235	2.0
ATWB 10-7L24	470	0.9	ATWB 10-7L24-Z	235	2.0
ATWB 10-7M24	470	0.9	ATWB 10-7M24-Z	235	2.0
ATWB 10-3I36	470	0.6	ATWB 10-3I36-Z	235	1.2
ATWB 10-3J36	470	0.6	ATWB 10-3J36-Z	235	1.2
ATWB 10-3K36	470	0.6	ATWB 10-3K36-Z	235	1.2
ATWB 10-3L36	470	0.6	ATWB 10-3L36-Z	235	1.2
ATWB 10-3M36	470	0.6	ATWB 10-3M36-Z	235	1.2
ATWB 10-3N36	470	0.6	ATWB 10-3N36-Z	235	1.2
ATWB 10-4I36	470	0.7	ATWB 10-4I36-Z	235	1.5
ATWB 10-4J36	470	0.7	ATWB 10-4J36-Z	235	1.5
ATWB 10-4K36	470	0.7	ATWB 10-4K36-Z	235	1.5
ATWB 10-4L36	470	0.7	ATWB 10-4L36-Z	235	1.5
ATWB 10-4M36	470	0.7	ATWB 10-4M36-Z	235	1.5
ATWB 10-4N36	470	0.7	ATWB 10-4N36-Z	235	1.5
ATWB 10-5I36	470	0.9	ATWB 10-5I36-Z	235	1.8
ATWB 10-5J36	470	0.9	ATWB 10-5J36-Z	235	1.8
ATWB 10-5K36	470	0.9	ATWB 10-5K36-Z	235	1.8
ATWB 10-5L36	470	0.9	ATWB 10-5L36-Z	235	1.8
ATWB 10-5M36	470	0.9	ATWB 10-5M36-Z	235	1.8
ATWB 10-5N36	470	0.9	ATWB 10-5N36-Z	235	1.8
ATWB 10-6I36	470	1.0	ATWB 10-6I36-Z	235	2.1
ATWB 10-6J36	470	1.0	ATWB 10-6J36-Z	235	2.1
ATWB 10-6K36	470	1.0	ATWB 10-6K36-Z	235	2.1
ATWB 10-6L36	470	1.0	ATWB 10-6L36-Z	235	2.1
ATWB 10-6M36	470	1.0	ATWB 10-6M36-Z	235	2.1
ATWB 10-6N36	470	1.0	ATWB 10-6N36-Z	235	2.1
ATWB 10-7I36	470	1.2	ATWB 10-7I36-Z	235	2.5
ATWB 10-7J36	470	1.2	ATWB 10-7J36-Z	235	2.5
ATWB 10-7K36	470	1.2	ATWB 10-7K36-Z	235	2.5
ATWB 10-7L36	470	1.2	ATWB 10-7L36-Z	235	2.5
ATWB 10-7M36	470	1.2	ATWB 10-7M36-Z	235	2.5
ATWB 10-7N36	470	1.2	ATWB 10-7N36-Z	235	2.5
ATWB 20-3I12	470	0.5	ATWB 20-3I12-Z	235	1.0
ATWB 20-3J12	470	0.5	ATWB 20-3J12-Z	235	1.0
ATWB 20-3K12	470	0.5	ATWB 20-3K12-Z	235	1.0
ATWB 20-3L12	470	0.5	ATWB 20-3L12-Z	235	1.0
ATWB 20-3M12	470	0.5	ATWB 20-3M12-Z	235	1.0
ATWB 20-4I12	470	0.6	ATWB 20-4I12-Z	235	1.2
ATWB 20-4J12	470	0.6	ATWB 20-4J12-Z	235	1.2
ATWB 20-4K12	470	0.6	ATWB 20-4K12-Z	235	1.2
ATWB 20-4L12	470	0.6	ATWB 20-4L12-Z	235	1.2
ATWB 20-4M12	470	0.6	ATWB 20-4M12-Z	235	1.2
ATWB 20-5I12	470	0.7	ATWB 20-5I12-Z	235	1.5
ATWB 20-5J12	470	0.7	ATWB 20-5J12-Z	235	1.5
ATWB 20-5K12	470	0.7	ATWB 20-5K12-Z	235	1.5
ATWB 20-5L12	470	0.7	ATWB 20-5L12-Z	235	1.5

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 20-5M12	470	0.7	ATWB 20-5M12-Z	235	1.5
ATWB 20-6I12	470	0.8	ATWB 20-6I12-Z	235	1.7
ATWB 20-6J12	470	0.8	ATWB 20-6J12-Z	235	1.7
ATWB 20-6K12	470	0.8	ATWB 20-6K12-Z	235	1.7
ATWB 20-6L12	470	0.8	ATWB 20-6L12-Z	235	1.7
ATWB 20-6M12	470	0.8	ATWB 20-6M12-Z	235	1.7
ATWB 20-7I12	470	0.9	ATWB 20-7I12-Z	235	2.0
ATWB 20-7J12	470	0.9	ATWB 20-7J12-Z	235	2.0
ATWB 20-7K12	470	0.9	ATWB 20-7K12-Z	235	2.0
ATWB 20-7L12	470	0.9	ATWB 20-7L12-Z	235	2.0
ATWB 20-7M12	470	0.9	ATWB 20-7M12-Z	235	2.0
ATWB 20-3I18	470	0.6	ATWB 20-3I18-Z	235	1.2
ATWB 20-3J18	470	0.6	ATWB 20-3J18-Z	235	1.2
ATWB 20-3K18	470	0.6	ATWB 20-3K18-Z	235	1.2
ATWB 20-3L18	470	0.6	ATWB 20-3L18-Z	235	1.2
ATWB 20-3M18	470	0.6	ATWB 20-3M18-Z	235	1.2
ATWB 20-3N18	470	0.6	ATWB 20-3N18-Z	235	1.2
ATWB 20-4I18	470	0.7	ATWB 20-4I18-Z	235	1.5
ATWB 20-4J18	470	0.7	ATWB 20-4J18-Z	235	1.5
ATWB 20-4K18	470	0.7	ATWB 20-4K18-Z	235	1.5
ATWB 20-4L18	470	0.7	ATWB 20-4L18-Z	235	1.5
ATWB 20-4M18	470	0.7	ATWB 20-4M18-Z	235	1.5
ATWB 20-4N18	470	0.7	ATWB 20-4N18-Z	235	1.5
ATWB 20-5I18	470	0.9	ATWB 20-5I18-Z	235	1.8
ATWB 20-5J18	470	0.9	ATWB 20-5J18-Z	235	1.8
ATWB 20-5K18	470	0.9	ATWB 20-5K18-Z	235	1.8
ATWB 20-5L18	470	0.9	ATWB 20-5L18-Z	235	1.8
ATWB 20-5M18	470	0.9	ATWB 20-5M18-Z	235	1.8
ATWB 20-5N18	470	0.9	ATWB 20-5N18-Z	235	1.8
ATWB 20-6I18	470	1.0	ATWB 20-6I18-Z	235	2.1
ATWB 20-6J18	470	1.0	ATWB 20-6J18-Z	235	2.1
ATWB 20-6K18	470	1.0	ATWB 20-6K18-Z	235	2.1
ATWB 20-6L18	470	1.0	ATWB 20-6L18-Z	235	2.1
ATWB 20-6M18	470	1.0	ATWB 20-6M18-Z	235	2.1
ATWB 20-6N18	470	1.0	ATWB 20-6N18-Z	235	2.1
ATWB 20-7I18	470	1.2	ATWB 20-7I18-Z	235	2.5
ATWB 20-7J18	470	1.2	ATWB 20-7J18-Z	235	2.5
ATWB 20-7K18	470	1.2	ATWB 20-7K18-Z	235	2.5
ATWB 20-7L18	470	1.2	ATWB 20-7L18-Z	235	2.5
ATWB 20-7M18	470	1.2	ATWB 20-7M18-Z	235	2.5
ATWB 20-7N18	470	1.2	ATWB 20-7N18-Z	235	2.5
ATWB 20-3I24	470	0.1	ATWB 20-3I24-Z	235	0.3
ATWB 20-3J24	470	0.1	ATWB 20-3J24-Z	235	0.3
ATWB 20-3K24	470	0.1	ATWB 20-3K24-Z	235	0.3
ATWB 20-3L24	470	0.1	ATWB 20-3L24-Z	235	0.3
ATWB 20-3M24	470	0.1	ATWB 20-3M24-Z	235	0.3
ATWB 20-4I24	470	0.2	ATWB 20-4I24-Z	235	0.3
ATWB 20-4J24	470	0.2	ATWB 20-4J24-Z	235	0.3
ATWB 20-4K24	470	0.2	ATWB 20-4K24-Z	235	0.3
ATWB 20-4L24	470	0.2	ATWB 20-4L24-Z	235	0.3
ATWB 20-4M24	470	0.2	ATWB 20-4M24-Z	235	0.3
ATWB 20-5I24	470	0.2	ATWB 20-5I24-Z	235	0.4
ATWB 20-5J24	470	0.2	ATWB 20-5J24-Z	235	0.4
ATWB 20-5K24	470	0.2	ATWB 20-5K24-Z	235	0.4

Evapco ATWB Pressure Drop Chart

Water as working fluid

Standard Flow			Series Flow		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 20-5L24	470	0.2	ATWB 20-5L24-Z	235	0.4
ATWB 20-5M24	470	0.2	ATWB 20-5M24-Z	235	0.4
ATWB 20-6I24	470	0.2	ATWB 20-6I24-Z	235	0.5
ATWB 20-6J24	470	0.2	ATWB 20-6J24-Z	235	0.5
ATWB 20-6K24	470	0.2	ATWB 20-6K24-Z	235	0.5
ATWB 20-6L24	470	0.2	ATWB 20-6L24-Z	235	0.5
ATWB 20-6M24	470	0.2	ATWB 20-6M24-Z	235	0.5
ATWB 20-7I24	470	0.3	ATWB 20-7I24-Z	235	0.6
ATWB 20-7J24	470	0.3	ATWB 20-7J24-Z	235	0.6
ATWB 20-7K24	470	0.3	ATWB 20-7K24-Z	235	0.6
ATWB 20-7L24	470	0.3	ATWB 20-7L24-Z	235	0.6
ATWB 20-7M24	470	0.3	ATWB 20-7M24-Z	235	0.6
ATWB 20-3I36	470	0.2	ATWB 20-3I36-Z	235	0.3
ATWB 20-3J36	470	0.2	ATWB 20-3J36-Z	235	0.3
ATWB 20-3K36	470	0.2	ATWB 20-3K36-Z	235	0.3
ATWB 20-3L36	470	0.2	ATWB 20-3L36-Z	235	0.3
ATWB 20-3M36	470	0.2	ATWB 20-3M36-Z	235	0.3
ATWB 20-3N36	470	0.2	ATWB 20-3N36-Z	235	0.3
ATWB 20-4I36	470	0.2	ATWB 20-4I36-Z	235	0.4
ATWB 20-4J36	470	0.2	ATWB 20-4J36-Z	235	0.4
ATWB 20-4K36	470	0.2	ATWB 20-4K36-Z	235	0.4
ATWB 20-4L36	470	0.2	ATWB 20-4L36-Z	235	0.4
ATWB 20-4M36	470	0.2	ATWB 20-4M36-Z	235	0.4
ATWB 20-4N36	470	0.2	ATWB 20-4N36-Z	235	0.4
ATWB 20-5I36	470	0.2	ATWB 20-5I36-Z	235	0.5
ATWB 20-5J36	470	0.2	ATWB 20-5J36-Z	235	0.5
ATWB 20-5K36	470	0.2	ATWB 20-5K36-Z	235	0.5
ATWB 20-5L36	470	0.2	ATWB 20-5L36-Z	235	0.5
ATWB 20-5M36	470	0.2	ATWB 20-5M36-Z	235	0.5
ATWB 20-5N36	470	0.2	ATWB 20-5N36-Z	235	0.5
ATWB 20-6I36	470	0.3	ATWB 20-6I36-Z	235	0.6
ATWB 20-6J36	470	0.3	ATWB 20-6J36-Z	235	0.6
ATWB 20-6K36	470	0.3	ATWB 20-6K36-Z	235	0.6
ATWB 20-6L36	470	0.3	ATWB 20-6L36-Z	235	0.6
ATWB 20-6M36	470	0.3	ATWB 20-6M36-Z	235	0.6
ATWB 20-6N36	470	0.3	ATWB 20-6N36-Z	235	0.6
ATWB 20-7I36	470	0.3	ATWB 20-7I36-Z	235	0.7
ATWB 20-7J36	470	0.3	ATWB 20-7J36-Z	235	0.7
ATWB 20-7K36	470	0.3	ATWB 20-7K36-Z	235	0.7
ATWB 20-7L36	470	0.3	ATWB 20-7L36-Z	235	0.7
ATWB 20-7M36	470	0.3	ATWB 20-7M36-Z	235	0.7
ATWB 20-7N36	470	0.3	ATWB 20-7N36-Z	235	0.7
ATWB 7-3H9	350	1.3	ATWB 7-3H9-Z	175	2.6
ATWB 7-3I9	350	1.3	ATWB 7-3I9-Z	175	2.6
ATWB 7-4I9	350	1.6	ATWB 7-4I9-Z	175	3.4
ATWB 7-4J9	350	1.6	ATWB 7-4J9-Z	175	3.4
ATWB 7-5I9	350	2.0	ATWB 7-5I9-Z	175	4.1
ATWB 7-5J9	350	2.0	ATWB 7-5J9-Z	175	4.1
ATWB 7-6J9	350	2.3	ATWB 7-6J9-Z	175	4.9
ATWB 7-3J12	350	1.4	ATWB 7-3J12-Z	175	3.0
ATWB 7-4J12	350	1.9	ATWB 7-4J12-Z	175	3.9
ATWB 7-5J12	350	2.3	ATWB 7-5J12-Z	175	4.8
ATWB 7-5K12	350	2.3	ATWB 7-5K12-Z	175	4.8
ATWB 7-6K12	350	2.7	ATWB 7-6K12-Z	175	5.7

Evapco ATWB Pressure Drop Chart

Water as working fluid

<i>Standard Flow</i>			<i>Series Flow</i>		
Model Number	Flow Rate (GPM)	Pressure Drop (PSI)	Model Number	Flow Rate (GPM)	Pressure Drop (PSI)
ATWB 7-5J14	350	2.5	ATWB 7-5J14-Z	175	5.2
ATWB 7-5K14	350	2.5	ATWB 7-5K14-Z	175	5.2
ATWB 7-6K14	350	2.9	ATWB 7-6K14-Z	175	6.2
ATWB 7-6L14	350	2.9	ATWB 7-6L14-Z	175	6.2
ATWB 7-3H18	350	1.8	ATWB 7-3H18-Z	175	3.8
ATWB 7-3I18	350	1.8	ATWB 7-3I18-Z	175	3.8
ATWB 7-4I18	350	2.3	ATWB 7-4I18-Z	175	4.9
ATWB 7-4J18	350	2.3	ATWB 7-4J18-Z	175	4.9
ATWB 7-5I18	350	2.9	ATWB 7-5I18-Z	175	6.0
ATWB 7-5J18	350	2.9	ATWB 7-5J18-Z	175	6.0
ATWB 7-6I18	350	3.4	ATWB 7-6I18-Z	175	7.2
ATWB 7-6J18	350	3.4	ATWB 7-6J18-Z	175	7.2