


UNIT	CONDENSER		EVAPCO, INC.  [®]	DWG. #	WB3171208-DRD-ST	REV.
MODEL #	ATC-639E	SCALE NTS		SERIAL #		DATE 2/7/2026

- NOTES:
- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B



evapco

DWG. # MVR2171200.DWG.CT


SERIAL #

REV.

DATE 2/7/2026


PLAN VIEW

FACE C



FACE D

FACE A



1'-7 8/8"
[327]

1'-3 5/8"
[397]

11'-11 3/4"
[3651]

FACE A

SHIPPING WEIGHT 23300 lbs+ [10570] kg+ OPERATING WEIGHT 31640 lbs+ [14355] kg+ HEAVIEST SECTION WEIGHT 9850 lbs+ [4470] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR