UNIT	CONDENSER		EVAPCO, INC. Evapco		DWG. # WB3122010-D	PRC-ST REV	
MODEL #	ATC-907E	SCALE NTS	EVAPC	O, INC.		SERIAL #	DATE 10/31/2025
2. HÉAV 3. MPT [FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APP FOR F PIPIN: 7. 3/4" [1 RECO	AN MOTOR LOCATION IEST SECTION IS UPPER SE DENOTES MALE PIPE THRE DENOTES FEMALE PIPE THRE DENOTES BEVELED FOR W DENOTES BEVELED FOR W DENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR) -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 ROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONN G 9mm] DIA. MOUNTING HOLE MMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	AD EAD EAD ELDING DE DE DRAWINGS) 44 kPa] NOT USE JECTING ES. REFER TO T DRAWING.		FACE B PLAN VIEW		FACE C ACCESS DOOR FACE A	FACE D
	mz ma įmmį		7"			I AGE A	
			7" [178]	1'-3 1/4" [387]	'¬		
	JCT		<u> </u>				
		5'-9 1/4" *	3'-3/8" *			(*)	
	3'-3 1/4" * (2) 4" [997] (2) 4" [10	[100] PE REFRIG IN REFRIG OL	9'-8 5/8" [2964] T	7/8" 8]		4	
	2" [50] MPT — MAKE-UP — MAKE-UP — 2'-1 1/4" [643]		6"-2 1/4" [1884]				
	[92] -	0] MPT					
	4: [1	1/4" 08] 7'-2" 2184]					
	-	11'-10" [3607] FACE B		2'-1/2" [622]	-	20'-0" [6096] FACE A	-