
JNIT CONDENSER			EVADOO TNO	evapco	DWG. #	DWG. # WB3243612-DRC-ST		REV.		
MODEL #	ATC-3313E	SCALE NTS	EVAPCO,	TINC.		SERIAL #	SERIAL #		DATE 11/1/2025	
2. HEAVIE 3. MPT DE FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT N ACCES 5. MAKE-I 20 psi N 6. *-APPR FOR PE PIPING 7. 3/4" [19 RECON	N MOTOR LOCATION ST SECTION IS UPPER ENOTES MALE PIPE THE NOTES FEMALE PIPE TE ENOTES BEVELED FOR ENOTES GROOVED NOTES FLANGE IOTES PLAIN END VEIGHT DOES NOT INC SORIES (SEE ACCESSO JP WATER PRESSURE IIN [137 kPa], 50 psi MA) OXIMATE DIMENSIONS RE-FABRICATION OF CO mm] DIA. MOUNTING HO IMENDED STEEL SUPPO SIONS LISTED AS FOLLE ENGLISH FT-IN METRIC [mm]	READ HREAD WELDING LUDE DRY DRAWINGS) ([344 kPa] DO NOT USE UNNECTING DLES. REFER TO DRT DRAWING.	PLA	FACE B		FACE A	(4) ACCESS DOOR		FACE D	
		5'-9 1/4 -+ 5'-9 1/5	7" [178] 3'-3/8" * [924]	1'-3 1/4" [387]				⊣		



166480 lbs+ [75515] kg+

HEAVIEST SECTION WEIGHT

26700 lbs+ [12115] kg+

OPERATING WEIGHT

123080 lbs+ [55830] kg+

SHIPPING WEIGHT DRAWN BY: SLR

NO. OF SHIPPING SECTIONS