CONDENSER		EVADCO	TNIC	evapc		CW4C141406-DRB-ST	REV -
ATC-535E SCALE N	rs	EVAPCO,	TIAC.		9	SERIAL#	DATE: 11/5/2025
NOTES  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS FAN/CASING SECT  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWIR  5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  6. *-APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING PIPING  7. 3/4" [19mm] DIA. MOUNTING HOLES. REFEI RECOMMENDED STEEL SUPPORT DRAWIR  8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	NGS) E R TO		* ^	FACE B PLAN VIEW	C C C C C C C C C C C C C C C C C C C	FACE C  (M)  ACCESS DOOR  SS DOOR  (M)  FACE A	<u>FACE D</u>
2'-0 3/8" [619] 6'-10 7/8" [2105] 6'-11 3/4" [2127] 7'-4"	(a) e' (100) PE REPRIO IN RETRIC OUT  (a) e' (20) PE REPRIO IN RETRIC OUT  (2) 2" [50] MPT MAKE-UP  (2) 2" [50] MPT DRAIN  5 1/8" [130] /8"	1'-10 7/8" * [581]  2'-11 3/8" [899]  (M)  4'-0 7/8" [1241]  12'-6 1/2" [3  5'-6 1/4" [1683]  1'-3" [381]  (2) 3" [80] MPT OVERFLOW	822]	1'-5 1/ [435	/8"	13'-11 3/4" [4261]	
## FACE  SHIPPING WEIGHT 21140 lbs+ [9590] kg+		22750 lbs+ [10320] kg+	HEAVIEST SECTI WEIGHT	ON ชุวชุก Ih	s+ [3805] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG